PASTERNACK
an INFINITE brand

The Engineer's Immediate RF Source



2023 Product Guide

50TH ANNIVERSARY EDITION





With Over 45 Years of RF Expertise, It's More Than Parts That Sets Us Apart

Since 1972, Pasternack has been satisfying the urgent requirements of engineers around the world by offering the largest in-stock, ready-to-ship selection of RF, microwave, and mmWave components, assemblies and devices, including over 40,000 popular and hard-to-find items across 107 categories of interconnect, passives, actives, antennas, and test and measurement. Ranging from DC to 220 GHz maximum frequency levels, Pasternack components are used in a wide range of test, development and deployment environments for military/aerospace, telecom, commercial, and industrial applications.

- 99.4% in-stock availability
- Same-day shipping
- No minimum order quantity
- 24/7 assistance by phone, email or chat
- Engineers on-hand to answer questions
- International distribution partner network



Largest RF Selection Available for Same-Day Shipping

- Adapters
- Amplifiers
- Antennas
- Attenuators/Equalizers
- Baluns
- Bias Tees/DC Blocks
- Cable Assemblies
- Cables
- Connectors
- Connector Accessories
- Couplers
- Educational Products
- Filters
- Frequency Multipliers/Dividers
- Impedance Matching
- Isolators/Circulators
- Limiters/Detectors
- Mixers/Modulators
- Noise Sources
- Oscillators/Synthesizers
- Phase Shifters/Trimmers
- Power Dividers/Combiners
- Rotary Joints
- Surge Protectors
- Switches
- Terminations
- Test and Measurement
- Tools
- Waveguides
- 60 GHz Systems & Modules



PE PASTERNACK
an INFINITE brand

Expanded Portfolio of High Frequency Components

In Stock and Available for Same-Day Shipping!

Pasternack's RF Engineering team has curated a broad portfolio of microwave and millimeter wave components to address the needs of 5G innovation and testing, along with other applications requiring higher frequencies and greater bandwidth. Whether your high frequency requirements are for active, passive, or interconnect products, Pasternack has you covered with the industry's largest in-stock selection available for same-day shipping.

Waveguide Components to 220 GHz



Electromechanical Switches to 50 GHz

Waveguide Electromechanical Switches to 40 GHz



Test Cables and Adapters 2.92mm/40 GHz, 2.4mm/50 GHz 1.85mm/70 GHz, 1.0mm/110 GHz



Broadband Amplifiers to 86.5 GHz



Mixers and Detectors to 110 GHz



PIN Diode Switches to 67 GHz



High Frequency Power Dividers/ Couplers to 67 GHz



Calibrated Noise Sources to 60 GHz



High Band 5G 28 GHz and 39 GHz



RF PRODUCT GUIDE INDEX

Failsafe Waveguide Electromechanical Switches; Field Replaceable Connectors and Launch Accessories; Outdoor Omnidirectional Antennas for 5G Networks; Expanded Line of Low-PIM and Low Loss Coaxial Cables; Variable Gain Amplifiers; High Quality Voltage Controlled Oscillators; etc.	3	NEW PRODUCT ADDITIONS
5G Solution from Pasternack	5	5G SOLUTIONS
Adapter Selection Guide; Adapter Locator (Part Number Identifier); Low PIM Adapters, Adapters to all Connectors	9	ADAPTERS
Amplifiers Selection Guide; Bi-Directional Amplifiers; Broadband Amplifiers; DC Coupled Amplifiers; Gain Block Amplifiers; Limiting Amplifiers; Linear Amplifiers; Log Amplifiers; Low Noise Amplifiers; Power-GaN Amplifiers; Rackmount Variable Gain Amplifiers; Amplifiers Accessories	50	AMPLIFIERS
Directional Antennas; Omni Directional Antennas; Antenna Mounts	62	ANTENNAS
Attenuators Selection Guide; Continuously Variable Attenuators; DC Bias Attenuators; Fixed Attenuators; Step Attenuators; TTL, CMOS, Relay and USB Attenuators; Voltage Variable Attenuators; Positive Slope Equalizers	72	ATTENUATORS & EQUALIZERS
Baluns	92	BALUNS
Bias Tees; DC Blocks	92	BIAS TEES & DC BLOCKS
Cable Assemblies Selection Guide; Cable Assemblies Locator (By Connector Type); High Reliability and Low PIM Cable Assemblies, Precision and Standard Cable Assemblies	94	CABLE ASSEMBLIES
Circulators; Isolators	224	CIRCULATORS & ISOLATORS
75 Ohm Broadcast; Communications; High Performance; RG MIL-C-17 Type Cables; Semi-Rigid & Formable; Twinax	227	COAX CABLES
Connector Selection Guide; Connector Locator (By Connector Type); All Connectors; Non-Shorting Caps; Shorting Caps; Launch Pins	234	CONNECTORS
Dual Directional Couplers; Single Directional Couplers; 90 Degree and 180 Degrees Hybrids	307	COUPLERS & HYBRIDS
RF Diplexers	312	RF DIPLEXERS
Bandpass Filters; Highpass Filters; Lowpass Filters; Band Pass Filters; Band Reject Filters; Harmonic Filters	313	FILTERS
Mixers and Bi-Phase Modulators; Frequency Dividers; Frequency Multipliers	316	FREQ. CONVERSION COMPONENTS
Hi-REL Limiters; PIN-PIN Limiters; PIN-Schottky Limiters; Biased Detectors, Finline Detectors, Log Detectors; Phase Detectors, Power Detectors; Schottky Zero Bias Detectors; Threshold Detectors; Tunnel Diode Zero Bias Detectors	318	LIMITERS & DETECTORS
Precision and Standard Noise Sources	321	NOISE SOURCES
Adjustable Phase Shifters and Trimmers; 8 Bit Programmable Phase Shifters; Analog Phase Shifters	322	PHASE SHIFTERS/ TRIMMERS
Resistive and Reactive Power Dividers; Wilkinson Power Dividers; Broadband	323	POWER DIVIDERS & RF COMBINERS
Rotary Joints	326	ROTARY JOINTS
In-Line Surge Protectors; Replacement Cartridges	326	SURGE PROTECTORS
Electromechanical Relay Switches; SMT Packaged Electromechanical Relay Switches; Manual Switches; High Isolation USB Switches; High Isolation Switches; PIN Diode Switches GaN High Power Switches	328	SWITCHES
Synthesizers; Commercial Surface Mount Packaged VCO; Hermatically Sealed MIL Grade Surface Mount Packaged VCO; Connectorized Packaged VCO, Reference Oscillators, TCXO Oscillators, Phase Locked Oscillators and Phase Locked Crystal Oscillators	340	SYNTHESIZERS & OSCILLATORS
Equal Split; Unequal Split	345	TAPPERS
RF Load Terminations; Feed-Thru Load Terminations; Resistive Impedance Transformers	347	TERMINATIONS & MATCHING PADS
1.0mm Flexible VNA Test Cables; 26.5, 40, 50, 67 GHz and 75 Ohm Test Cables; Calibration Kits; Handheld RF Analyzer Rugged Stable Cable Assemblies; PE-TC151 and PE-TC195 Series Phase Stable Test Cable Assemblies; Semi-Rigid Pigtail Test Probes; VNA Test Cable Assemblies, etc.	353	TEST & MEASUREMENT PRODUCTS
Cable Cutters; Crimp Tools; Crimp Tool Dies ; Insertion/Extraction Tools; Torque Wrenches	359	TOOLS
WG Antennas; WG Bandpass Filters; WG Bends; WG Bulkhead Adapters; WG Converters; WG Couplers; WG Detectors; WG Direct Read Atten.; WG EMS; Flexible WG; WG Gunn Oscillators; WG Magic Tees; WG Phase Shifters; WG PIN Diode Switches; WG Power Amps., etc.	362	WAVEGUIDES
Pasternack REACH and RoHS Compliance Programs; Mailing List Changes; Binding Terms/Warranty; Part Number Index; Mounting Holes; Connector Identifiers; Connector Frequency Range Chart; Conversion Tables	399	APPENDIX

The information contained in this catalog and on pasternack.com is accurate to the best of our knowledge at the time of publication. It may be necessary to make modifications to the parts and/or the documentation of the parts, in order to implement improvements. Pasternack reserves the right to make such changes as required. Pasternack does not make any representation or warranty regarding the suitability of the parts described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any parts or documentation.

TABLE OF CONTENTS

5G Solutions
- The 5G Outlook....5
- RF Interconnects....6
- RF Actives....6
- RF Passives....7
- Antennas....8

Adapters
- Adapters to All Connectors....18
- Locator (Part Number Identifier)....10
- Low PIM Adapters....16
- Quick Reference Guide....9
- Selection Guide....9

Amplifiers
- Locator....50
- Quick Reference Guide....50
- Selection Guide....50
- Bi Directional Amplifiers....52
- Broadband Amplifiers....52
- DC Coupled Amplifiers....54
- Gain Block Amplifiers....54
- GaN Power Amplifiers....60
- Input Protected Low Noise Amplifiers....56
- Limiting Amplifiers....55
- Log Amplifiers....55
- Low Noise Amplifiers....55
- Power Amplifiers....57
- Temperature Compensated Amplifiers....57
- Variable Gain Amplifiers....61
- Amplifier Accessories....61

Antennas
- Antenna Mounts....71
- Directional Antennas....62
- Omni Directional Antennas....64

Attenuators, Active
- Locator....72
- Quick Reference Guide....72
- Selection Guide....72
- Programmable Attenuators....90
- Voltage Variable Attenuators....91

Attenuators, Passive
- Locator....72
- Quick Reference Guide....72
- Selection Guide....72
- Continuously Variable Attenuators....90
- DC Bias Attenuators....89
- Fixed Attenuators....74
- Step Attenuators, Push Button....88
- Step Attenuators, Rotary....89
- Step Attenuators, Toggle....88

Baluns
- Surface Mount....92

Bias Tee
- 1.85mm....92
- 2.4mm....92
- 2.92mm....92
- 3.5mm....92
- N....92
- SMA....92

Cable Assemblies
- Locator (By connector Type)....95
- Low PIM and High-Reliability Cable Assemblies....99
- Precision and Standard Cable Assemblies....104
- Quick Reference Guide....94
- Selection Guide....94

Circulators
- 2.92mm Connectors....224
- N Connectors....224
- SMA Connectors....224

Coaxial Cables
- 75 Ohm Broadcast....228
- Communications....228
- High Performance....230
- RG Mil-C-17 Type Cable....230
- Semirigid and Formable....231
- Twinax Cable....233

Connectors
- Locator (Part Number Identifier)....234
- Quick Reference Guide....234
- Selection Guide....234
- Launch Pins....304

Connector Caps
- Non-Shorting Caps....305
- Shorting Caps....306

Couplers
- 90 degree Hybrid....311
- 180 degree Hybrid....312
- Directional....307
- Dual Directional....310

DC Blocks
- 1.85mm....93
- 2.4mm....93
- 2.92mm....93
- BNC....93
- F....93
- MCX....93
- N....93
- SMA....93
- TNC....93

Detectors
- Biased Detectors....319
- Finline Detectors....319
- Log Detectors....319
- Phase Detectors....320
- Power Detectors....320
- Schottky Zero Bias Detectors....320
- Threshold Detectors....320
- Tunnel Diode Zero Bias Detectors....320

RF Diplexers
- RF Diplexers....312

Equalizers
- Positive Slope Equalizers....91

Filters
- Band Pass....313
- Band Reject....313
- Chebyshev Filters....314
- Combline Filters....314
- High Pass Filters....315
- Low Pass Filters....315

Frequency Dividers
- SMA Connectors....315

Frequency Multipliers
- Active....317
- Passive Doublers....317

Isolators
- 2.4mm Connectors....225
- 2.92mm Connectors....225
- N Connectors....225
- SMA Connectors....225

Limiters
- High Rel....318
- PIN-PIN....318
- PIN-Schottky....319

Manual Switches
- Manual Switches....335

Matching Pads
- Resistive Impedance Transformers....352

Mixers
- Double Balanced....316
- IQ....316
- Triple Balanced....316

Modulators
- BiPhase....317

Noise Sources
- Precision....321
- Standard....321
- SMT Pin Packaged....321

Oscillators
- 0.175" Ultra Small Surface Mount Packaged VCO....341
- 0.5" Surface Mount Packaged VCO....341
- 0.5" Surface Mount Packaged VCO w/ Integrated Buffer Amps....342
- 0.5" Surface Mount Packaged VCO w/ Low Noise....342
- 0.5" Surface Mount Packaged VCO w/ Modulation Input Port....343
- 0.5" Hermetically Sealed MIL Grade Surface Mount Packaged VCO....343
- Connectorized Packaged VCO w/ Field Replaceable Connectors....343
- Phase Locked Crystal Oscillators....345
- Phase Locked Oscillators....345
- Reference Oscillators....344
- TCXO Reference Oscillators....344

Phase Shifters
- 8 Bit Programmable Phase Shifter....322
- Adjustable Phase Shifter....322
- Analog Phase Shifter....323

Phase Trimmers
- Adjustable Phase Trimmer....322

Power Dividers
- 323
- Reactive....324
- Resistive....323
- Wilkinson....325

RF Combiners
- Broadband....326

Rotary Joints
- 2.92mm-2.92mm....326
- SMA-PCB....326
- SMA-SMA....326

Surge Protectors
- In-Line Surge Protectors....326
- Surge Protector Replacement Cartridges....328

Switches
- Electromechanical Relay Switches....328
- Electromechanical Relay Switches, SMT Packaged....334
- GaN High Power Switches....340
- High Isolation PIN Diode Switches....339
- High Isolation USB PIN Diode Switches....339
- PIN Diode Switches....335

Synthesizers
- Integer/Fractional....341

Tappers
- Equal Split....345
- Unequal Split....346

Terminations
- Feed-Thru Load....351
- RF Load....347

Test And Measurement
- 26.5 GHz and 40 GHz Test Cables....355
- 40 GHz and 67 GHz Skew Matched Cable Pairs....355
- 50 GHz and 67 GHz Test Cable Assemblies....356
- 110 GHz 1.0mm Flexible VNA Precision Cables....356
- 4-in-1 Calibration Kits....354
- Bench Type Calibration Kits....353
- Handheld RF Analyzer Rugged Phase Stable Cable Assemblies....357
- Interchangeable Connectors....354
- PE-TC151 Series Phase Stable Test Cable Assemblies....358
- PE-TC195 Series Phase Stable Test Cable Assemblies....357
- Phase Stable Test Cable Assemblies-75 Ohm....358
- RF Microwave Probes....354
- Semi-Rigid Pigtail Test Probes....358
- VNA Test Cable Kit....355

Tools
- Crimp Tools....361
- Crimp Tool Dies....361
- Torque Wrenches....360

Waveguides
- Flexible Waveguides....386
- Waveguide Antennas....364
- Waveguide Antennas Accessories....372
- Waveguide BandPass Filters....376
- Waveguide Bends....376
- Waveguide Bulkhead Adapters....377
- Waveguide Circulators....378
- Waveguide Converter Mixers....378
- Waveguide Couplers....378
- Waveguide Detectors....384
- Waveguide Direct Read Attenuators....384
- Waveguide Double Ridge Bends....377
- Waveguide Electromechanical Relay Switches....384
- Waveguide Double Ridge EMS....385
- Waveguide Fixed Attenuators....386
- Waveguide Frequency Multipliers....388
- Waveguide Gunn Oscillators....388
- Waveguide Isolators....388
- Waveguide Low Noise Amplifiers....389
- Waveguide Magic Tees....389
- Waveguide Orthomode Transducers....389
- Waveguide Phase Shifters....390
- Waveguide PIN Diode Switches....390
- Waveguide Polarizers....390
- Waveguide Power Amplifiers....390
- Waveguide Rotary Joints....391
- Waveguide Sections....391
- Waveguide Terminations....393
- Waveguide Transitions....394
- Waveguide Twists....394
- Waveguide Variable Attenuators....395
- Waveguide Voltage Variable Attenuators....395
- Waveguide Accessories....396

HELPFUL RESOURCES

Connector Freq. Range Chart....424	Mounting Hole Layout....419
Connector Identifier....420	Part Number Index....404
Conversion Tables....417	REACH-RoHS Compliance Program....400
How to Place your Order....401	Terms & Conditions....401

NEW PRODUCT ADDITIONS

Failsafe Waveguide Electromechanical Switches (See pages 328)



- Comprehensive selection of 16 SPDT/DPDT models
- Broadband frequency covers popular X and Ka bands
- Designs support WR112, WR90, and WR28 waveguide sizes with O-Ring Grooves or CPR-Flat configurations
- TTL logic

Field Replaceable Connectors and Launch Accessories (See pages 234, 304)



- 4 Connector series SMA, 2.92mm, 2.4mm, and 1.85mm
- 2-Hole and 4-hole flange types
- Contacts mate with 5 pin diameters ranging from 0.009" to 0.036"
- Metal ground contact rings
- Allows for replacement of damaged connectors without accessing sealed components
- Multiple connector series can be used with a single mating pin diameter

Outdoor Omnidirectional Antennas for 5G Networks (See pages 62)



- Fiberglass PRO series models
- 8, 10, and 12 dBi options
- Suitable for SISO or MIMO operation
- Low-cost polycarbonate or ABS options
- Type N connectors

Expanded Line of Low-PIM, Low Loss Coaxial Cables (See pages 101)



- Over 400 unique configurations
- 10 Popular cable types
- 8 Connector series/ 90+ connectors
- Straight and right-angle connector bodies
- 1,000's of standard cables in stock
- 100% PIM tested
- PIM levels marked on each assembly

Variable Gain Amplifiers (See pages 61)



- Frequencies ranging from 500 MHz to 40 GHz
- GaAs FET semiconductor technology
- High Gain: 45 dB typical
- Variable gain control: 20 dB typical with 0 to +5V control voltage
- Noise Figure: 3.5 dB typical
- Output P1dB: 10 to 15 dBm typical
- Rugged Mil grade aluminum package designs support female SMA or 2.92mm spark plug connectors
- Designed to meet a series of environmental conditions including altitude, vibration, humidity and shock

High Quality Voltage Controlled Oscillators (See pages 328)



- Cover broad frequency bands ranging from 230 MHz to 5420 MHz
- Output power ranges from 0 dBm to +9 dBm
- Exceptional phase noise performance as low as -110 dBc/Hz at 10 KHz offset
- 50 ohm designs feature internal voltage regulation and reverse DC protection
- Compact and rugged SMA connectorized packages
- Operating Temperature Range: -40°C to +85°C

High-Reliability, COTS-Grade Components and Cable Assemblies



- Meets a series of MIL-STD environmental test conditions
- Ideal for test lab, IFF, SATCOM, ECM, EW, UAV, Radar, avionics, rail, automotive, oil & gas, chemical systems, and more
- Custom hi-rel cable assemblies, with MIL-SPEC and temperature conditioned options

Waveguide Loads (See pages 362)



- Waveguide sizes from WR-28 to WR284 (10 different waveguide bands)
- Power ratings ranging from 1W to 500W
- Copper and aluminum body options
- Excellent VSWR performance
- No minimum order quantities

High Reliability Cable Assemblies (See pages 99)



- These Hi-Rel assemblies are ideal for a wide variety of applications, including: IFF, SATCOM, UAV, Automotive, Oil & Gas, Railway

NEW PRODUCT ADDITIONS

Programmable Attenuators to 40 GHz (See pages 91)



- Covers DC to 40 GHz
- Offers designers flexibility with TTL, USB, or relay-controlled options
- Feature attenuation ranges from 31dB - 95dB with 0.5dB and 1dB step sizes

High-Power PIN Diode RF Switches (See pages 335)



- Available in SPDT and SP4T configurations
- Cover 30 MHz to 6 GHZ and feature reflective and absorptive designs
- Available in rugged MIL-Grade coaxial packages with an operational temperature range of -40° to +85°C

1.85mm Right Angle RF Adapters (See pages 18)



- Broadband mode free operation to 67 GHz
- Intermateable with 2.4mm connectors
- Robust stainless-steel construction for repeatability and reliability

NMD Adapters (See pages 9)



- Reduces wear on VNA test ports
- Maximum pressure up to 0.2MPa
- Allows adapting VNA test port to other connector types for Device Under Test (DUT) measurements

Waveguide Pressure Windows (See pages 397)



- Waveguide sizes from WR-28 to WR-340
- Maximum pressure up to 0.2MPa
- 1.25.1 maximum VSWR
- Maximum PSI 29

Waveguide Fixed Attenuators (See pages 386)



- Waveguide size from WR-10 to WR-28
- Maximum power rating up to 5W
- VSWR performance as low as 1.15:1

2.2-5 Low PIM RF Adapters (See pages 16)



- Operating Frequency up to 8 GHz
- Corrosion resistant tri-metal finish
- Broad cable selections
- Excellent VSWR of 1.25:1

5G Sub-6GHz Omni Antennas (See pages 62)



- 600 MHz to 3.8 GHz capability
- Rugged outdoor design
- 5G, 4G, LTE, CBRS, GSM, UMTS, PCS, Wi-Fi network capable
- Omnidirectional patterns
- N Type Female connectors

High Performance Couplers (See pages 307)



- Power ratings range from 10 Watts to 70 Watts
- Power tappers handle high power up to 300 W depending on style
- Frequency range from 1 GHz to 8 GHz, unequal RF tappers are more wide band with 380 MHz to 6 GHz based on model selected

RF Circulators and Isolators (See pages 224)



- Offered in SMA, N-type, 2.4mm and 2.92mm connectorized designs
- Dual junction and single junction selections are available
- Minimize loss when transmitting input signals from one port to another
- Excellent VSWR and isolation

High Quality Noise Generators (See pages 321)



- Operating frequencies ranging from 1 GHz to 18 GHz
- Portfolio supporting sub-6 GHz and millimeter-wave frequency bands
- Output ENR levels from 15.5 dB to 35 dB
- Rugged metal packaging
- A variety of DC and output RF connector options

Temp. Compensated Amplifiers (See pages 57)



- Frequencies range: 500 MHz to 40 GHz
- Operating temperature range: -55°C to +85°C
- Utilize pin diode attenuation circuitry

Times Microwave Bulk Coax Cable (See pages 227)



- Low loss
- Double shielded
- Operating Frequency up to 5.8 GHz
- TPE cable jackets
- Ultra-Flexible and Fire Rated options

Hand Formable Test Probe Cables (See pages 354)



- 100% RF Tested prior to final trim
- 1.4 Max VSWR to 20 GHz
- 100% High Pot Tested to 500V
- Unterminated cable end can attach to PCB boards
- Individually packed in protective tube

Waveguide Gunn Diode Oscillators (See pages 388)



- WR-90, WR-42, WR-28 support X, K, and Ka bands
- Package designs support mechanical tuning screws
- Output power levels up to +13 dBm typical
- Incorporate Indium Phosphide (InP) Gunn Diodes
- Designed to meet MIL-STD-202 Environmental Test Conditions

Frequency Doublers and Triplers (See pages 316)



- Frequency bands: 10 MHz to 16 GHz
- Input Drives level: 10 to 20 dBm
- 15 dB conversion loss and up to 45 dB fundamental isolation
- Active frequency tripler: 250 MHz to 1500 MHz with -3 to 0 dBm input drive levels
- Conversion gain of 4-12 dB and up to 45 dB



The 5G Outlook

5G promises to deliver lightning-speed data rates, increased user capacity, reduced latency, and overall improved network efficiencies through new delivery technologies and distribution techniques like network splicing. Although many factors affect network speed, 5G will be at least 10 times faster than 4G networks, which often average less than 10 Mbps.
The global 5G infrastructure being built today will be the backbone of RF wireless innovation for years to come and also enable a new era for big data, where near-real-time processing and intelligence shared to and from a pleothera of connected devices will provide enhanced user experiences, safety, and responsiveness.

New 5G devices and applications are in various stages of development, testing and deployment. Three major use cases for 5G have been defined:

Mission Critical Applications

Including autonomous vehicles, remote health care, intelligent grids, industrial automation, and more – where low latency, ultra-high reliability connectivity is essential.

Enhanced Mobile Broadband

Offering increased speed and capacity through further rollout of MIMO, small cell, DAS, and fixed wireless technologies.

The Internet of Things (IoT)

Comprised of billions of connected devices, communicating without human intervention, creating new opportunities for big data exchange and analysis, and set to revolutionize manufacturing, business communications, agriculture, and more.

5G Solutions from Pasternack

RF Components for the Next Generation.....see web

Pasternack meets the urgent needs of engineers and technicians around the world for high-grade RF components and cable assemblies to support 5G innovation development, testing and deployments in the global sub-6 GHz (e.g. the 3.5 GHz mid-band) and mmWave bands (e.g. 26 GHz, 28 GHz and 39 GHz).

All Pasternack 5G solutions components are in-stock and shipped same day, and they are backed by first-class technical and engineering support. Our applications engineers are standing by ready to assist with answering your questions and selecting the right product for your specific application. Visit us online at Pasternack.com to view detailed datasheets, CAD drawings, real-time pricing and inventory, or to place your order and have it shipped today!

RF Interconnects

Connectors.....see web

Configure and customize your signal exactly as required with Pasternack's ready-to-ship RF connectors for 5G applications.

- A variety of options for size, frequency, signal power, PIM, durability, and space limitations
- Optimized for premium VSWR and PIM levels

Adapters.....see web


Get the reliable performance you expect and protect expensive test equipment with Pasternack's ready-to-ship RF adapters for 5G applications.

- A variety of options for size, frequency, signal power, PIM, durability, and space limitations
- Optimized for premium VSWR and PIM levels

Cable Assemblies.....see web

Count on the high-performance and rugged reliability of Pasternack's ready-to-ship RF cable assemblies for your 5G application.

- Low PIM in a variety of diameters and connector options
- Low VSWR and insertion loss
- Excellent phase stability under flexure
- Maximum operating frequencies up to 110 GHz, depending on cable type



5G Use Cases in a Shared

RF Actives

Amplifiers.....see web

Expect reliable signal amplification with Pasternack's ready-to-ship, connectorized RF amplifiers for 5G applications.

- Over 65 models ideal for sub-6 GHz and mmWave frequency bands
- Amplifier designs include: bench-top, broadband, gain block, GaN power, high power, input protected low noise, limiting, low noise, waveguide, power, rack mount, USB, variable gain

Phase Shifters / Trimmers.....see web

Reliably convert frequencies with Pasternack's ready-to-ship, high-quality RF phase shifters and trimmers for 5G applications

- Covering select frequency bands up to 40 GHz and adjustable up to 120 degrees
- Available in manual-programmable varieties

Switches.....see web

Meet your signal processing requirements with Pasternack's ready-to-ship RF electromechanical relay and PIN diode switches for 5G applications.

- Covering broadband frequencies DC to 40 GHz
- Over 165 models available in coaxial, waveguide, and SMT packaged configurations

Mixers and Multipliers.....see web

Expect high-performance signal conversion with Pasternack's ready-to-ship RF mixers and multipliers for 5G applications.

- Coaxial packaged mixers and multipliers covering select frequency bands from DC to 46 GHz
- Available in double-balanced, triple-balanced and IQ designs, with LO drive levels ranging from 10 to 19 dBm

Programmable Attenuators.....see web


Ensure reliable attenuation levels with Pasternack's ready-to-ship RF programmable attenuators for 5G applications.

- Covering sub-6 GHz and mmWave frequency bands
- Maximum attenuation levels up to 127 dB
- Designs optimized for low insertion loss and excellent VSWR as low as 1.25:1

Limiters and Detectors.....see web

Keep control of I/O power levels with Pasternack's ready-to-ship, broadband coaxial packaged RF limiters and detectors for 5G applications.

- Over 15 limiters and 20 detectors available for sub-6 GHz or mmWave frequency bands
- Available in compact cylindrical or drop-mountable package outlines with SMA or 2.92 mm RF connectors
- Ideal for proof-of-concept and prototyping in precision test and measurement, instrumentation, and subsystem assemblies



l Network Infrastructure

Noise Sources.....see web

Meet your immediate requirements for signal performance testing with Pasternack's ready-to-ship RF coaxial packaged noise sources for 5G applications.

- Over 25 models covering sub-6 GHz and mmWave frequency bands
- Noise source design configurations include: octave band and broadband, amplified, precision-calibrated instrumentation-grade, noise sources with integral isolators
- Most models designed to meet MIL-STD-202F environmental test conditions

Oscillators.....see web

Count on high-performance signal generation with Pasternack's ready-to-ship RF oscillators for 5G applications.

- Covering select bands from 10 MHz to 43 GHz
- Oscillator types include: voltage controlled (VCO), reference, phase locked, phase locked crystal, temperature compensated crystal
- Surface mount and coaxial packaged versions available

RF Passives

Power Dividers.....see web

Meet your immediate needs for 2-way and 4-way input power division with Pasternack's ready-to-ship RF power dividers for
5G applications.

- Maximum input power of 30 W for wideband operating frequency ranges up to 6 GHz
- Maximum input power of 20 W for operating frequency ranges in the mmWave bands

Fixed Attenuators.....see web

Provide reliable signal attenuation with Pasternack's line of ready-to-ship RF fixed attenuators for 5G applications.

- Wide range of attenuation levels and rated up to 2 W
- Maximum operating frequencies up to 6 GHz and mmWave bands
- Durable stainless steel construction
- Available in SMA and 2.92 mm connector designs

Terminations.....see web

Expect durable, high-performance with Pasternack's ready-to-ship RF terminations for 5G applications.

- Rated up to 2 W with maximum operating frequencies up to 6 GHz, 18 GHz, or 40 GHz
- Reliable stainless steel construction
- Available in SMA, Mini SMP, Type-N, 4.3-10, and 2.92 mm connector series

Filters.....see web

Turn to Pasternack for your RF bandpass filter needs for 5G applications.

- Covering mid-band and mmWave band frequencies
- 4, 9, and 11 section options
- SMA connector package design
- Low insertion loss and excellent VSWR

Directional Couplers.....see web

Expect high-quality signal coupling performance with Pasternack's ready-to-ship RF directional couplers for 5G applications.

- Wide range of coupling levels available and maximum input power levels as high as 30 W
- Operating frequency ranges up to the mmWave bands and operating temperature range from -45 to 85 degree C
- SMA and 2.92 connector designs available

Waveguides.....see web

Enable low loss transmission with Pasternack's ready-to-ship, precision waveguide components for 5G applications.

- mmWave operating frequency bands and Wide range of waveguide sizes
- Waveguide components include: couplers, waveguide-to-coax adapters, straights, bends, twists, and more

DC Blocks.....see web

Protect your bias-sensitive RF components with Pasternack's ready-to-ship, high-grade RF DC blocks for 5G applications.

- Maximum operating frequency ranges up to the mmWave band
- Inner or outer conductor configuration options available
- 2.92 mm, SMA, Type-N, and TNC connector designs available

Bias Tees.....see web

Ensure dependable signal processing with Pasternack's ready-to-ship RF bias tees for 5G applications.

- Maximum operating frequencies in the sub-6 GHz or mmWave frequency bands
- Maximum DC voltage rating of 100 V and current rating of 2.5 A
- SMA, Type-N, 3.5 mm, and 2.92 mm connector options available

5G Efficiencies

10x
Decrease in Latency
Delivering latency as low as 1 ms

3x
Spectrum Efficiency
Achieving even more bits per Hz with advanced antenna techniques

10x
Experience Throughput
Bringing more uniform, multi-Gbps peak rates

10x
Connection Density
Enabling more efficient signaling for IoT connectivity

100x
Traffic Capacity
Driving network hyper-densification with more small cells everywhere

100x
Network Efficiency
Optimizing network energy comsumption with more efficient processing

Antennas

RF and Waveguide Antennas.....see web

Explore Pasternack's wide selection of ready-to-ship RF and waveguide antennas for 5G applications.

- Operating in the sub-6 GHz and mmWave frequency bands
- Including coax fed antennas operating at sub-6 GHz
- Comprehensive offering of waveguide antennas including: standard gain horns, conical horns, scalar feed horns, lens horns, omni-directional with waveguide flanges
- Waveguide antennas mount directly to waveguides or can be combined with waveguide-to-coax adapters for coaxial connections

Adapter Selection Guide

3 Easy Ways to Find your Product.....

1. Search by PE Part Number

If you know the PE part number you are searching for, please reference our Part Number Index on Page 404

2. Quick Reference Guide

(Page number refers to first appearance of product in the Adapter Section)

Connector Series	Page
1.0/2.3	36
1.0mm	18
1.85mm	18
2.2-5	20
2.4mm	19
2.4mm NMD	20
2.92mm	19
2.92mm NMD	22
3.5mm	19
3.5mm NMD	22
4.1/9.5 Mini DIN	23
4.3-10	23

Connector Series	Page
7/16 DIN	24
10-32	26
75Ω BNC	45
75Ω F	27
75Ω Mini SMB	46
75Ω N	47
75Ω PAL	46
75Ω RCA	27
75Ω SMB	27
75Ω SMC	27
75Ω TNC	47
78Ω BNC Twinax	48

Connector Series	Page
7mm	21
95Ω 3/4"-20 Twinax	49
Banana	49
BMA	26
BNC	23
BNC Triax	26
C	27
Double Banana	26
D-Sub	27
FME	27
GR874	28
HN	25

Connector Series	Page
LC	28
MCX	29
MHV	27
Mini SMP	19
Mini UHF	29
MMBX	30
MMCX	30
N	19
QMA	34
Rev Pol MCX	41
Rev Pol N	34
Rev Pol SMA	40


Connector Series	Page
Rev Pol TNC	34
SC	25
SHV	29
SMA	20
SMB	32
SMC	32
SMP	20
SSMA	21
SSMB	38
SSMC	40
TNC	32
UHF	32
UMCX	38

Adapter Locator Layout

Connector Type	Feature	Model No.	C/R	Page
Indicates Connector Series Example: SMA, BNC,TNC, N	Contains a 1 or 2 Letter Code Example: (B) - Bulkhead (PO) - Push On	Adapter Part Number	Location of part on grid using Columns & Rows	Product Page Number

3. Between-Series Adapter Locator

(Adapter Locator starts on Page 10)



SMA FEMALE TO TNC FEMALE
PE9079

SMA Female To: EXAMPLE

Connector Type	Feature	Model No.	C/R	Page
SSMA Male		PE9188	A4	163
SSMB Plug		PE9402	A3	167
TNC Female		**PE9079**	D6	164
TNC Female	(B)	PE9251	A1	165

TNC Female To: EXAMPLE

Connector Type	Feature	Model No.	C/R	Page
SMA Female	(P)	PE9442	C6	164
SMA Female		**PE9079**	D6	164
SMA Female	(B)	PE9251	A1	165
SMA Female	(PM)	PE9276	B1	165

The Adapter Locator example above includes Between-Series part numbers in two configurations:
Connector 1 to Connector 2 as well as Connector 2 to Connector 1 can be found in the same location.

Products can only be found under the first instance of the series combination. As an example, PE9079 above will be found in only one location in the Adapter Section.

Adapter Locator

Connector Type	Feature	Model No.	C/R	Page
1.0/2.3 Jack To:				
SMA Female		PE9693	E2	38
SMA Male		PE9690	B4	36
1.0/2.3 Plug To:				
SMA Female		PE9691	D2	38
SMA Male		PE9692	A4	36
1.0mm Female To:				
1.85mm Female		PE91109	D5	18
1.85mm Male		PE91119	C5	18
1.0mm In-Series:				
Female to Female		PE91463	D4	18
Female to Male		PE91461	C4	18
Male to Male		PE91462	B4	18
1.0mm Male To:				
1.85mm Female		PE91108	B5	18
1.85mm Male		PE91118	A5	18
1.85mm Female To:				
1.0mm Female		PE91109	D5	18
1.0mm Male		PE91108	B5	18
2.4mm Female	90º	PE91534	E2	19
2.4mm Male		PE9674	C6	19
2.92mm Female	90º	PE91163	C3	19
2.92mm Female	90º	PE91513	D3	19
2.92mm Male	90º	PE91162	A3	19
2.92mm Male	90º	PE91512	B3	19
2.92mm Male		PE9666	A1	21
3.5mm Female		PE9748	D5	22
3.5mm Male		PE9745	A4	22
N Female		PE9721	A4	19
N Male		PE9720	E3	19
SMA Female		PE9729	B3	38
SMA Male		PE9728	D4	36
1.85mm In-Series:				
Female to Female		PE91084	B7	18
Female to Female		PE91115	C7	18
Female to Female	90º	PE1278	D7	18
Male to Female		PE91086	D6	18
Male to Female		PE9715	E6	18
Male to Female	90º	PE1276	A7	18
Male to Male		PE91085	A6	18
Male to Male		PE9716	B6	18
Male to Male	90º	PE1277	C6	18
1.85mm Male To:				
1.0mm Female		PE91119	C5	18
1.0mm Male		PE91118	A5	18
2.4mm Female	90º	PE91511	C1	19
2.4mm Female		PE9673	D7	19
2.4mm Female	(P)	PE91542	E7	19
2.4mm Male	90º	PE91157	A1	19
2.4mm Male	90º	PE91518	B1	19
2.4mm Male		PE9672	A6	19
2.4mm Male		PE91540	B6	19
2.92mm Female	90º	PE91527	A2	19
2.92mm Female		PE9665	B4	21
2.92mm Male	90º	PE91161	D1	19
2.92mm Male	90º	PE91519	E1	19
2.92mm Male		PE9667	E7	20
3.5mm Female		PE9747	B2	19
3.5mm Male		PE9746	E3	22
N Female		PE9719	D2	19
N Male		PE9718	C2	19
SMA Female		PE9726	A3	38
SMA Male		PE9727	C4	36
10-32 Female To:				
BNC Female		PE9752	C2	26
BNC Female	(B)	PE9754	D2	26
BNC Male		PE9750	B2	26
10-32 In-Series:				
Female to Female		PE9756	A1	26
Female to Female	(B)	PE9757	B1	26
10-32 Male To:				
BNC Female		PE9753	E1	26
BNC Female	(B)	PE9755	A2	26
BNC Male		PE9751	D1	26
2.2-5 Female To:				
7/16 DIN Male	(LP)	PE9799	A1	25
N Female	(LP)	PE9795	E1	34
N Male	(LP)	PE9797	B7	32
2.2-5 In-Series:				
Female to Female	(LP)	PE9793	B5	20
Male to Male	(LP)	PE9792	A5	20
2.2-5 Male To:				
7/16 DIN Male	(LP)	PE9798	E7	24
N Female	(LP)	PE9794	D1	34
N Male	(LP)	PE9796	A7	32
2.4mm Female To:				
1.85mm Female	90º	PE91534	E2	19
1.85mm Male		PE9673	D7	19
1.85mm Male	(P)	PE91542	E7	19
1.85mm Male	90º	PE91511	C1	19
2.4mm NMD Female		PE91145	C4	20
2.92mm Female	90º	PE91111	B1	20
2.92mm Female	90º	PE91525	C1	20
2.92mm Female		PE91499	A5	21
2.92mm Female		PE9456	B5	21
2.92mm Male	90º	PE91526	A1	20
2.92mm Male		PE91450	D1	21
2.92mm Male		PE9455	E1	21
2.92mm NMD Female		PE91144	B2	22
3.5mm Female		PE91291	A6	22
3.5mm Female		PE9652	B6	22
3.5mm Female		PE91547	C6	22
3.5mm Male		PE91452	D4	22
3.5mm Male		PE9651	E4	22
3.5mm NMD Female		PE91148	E1	23
Full Detent Mini SMP Male		PE91122	D1	20
Mini SMP Female		PE91123	E1	20
N Female	(P)	PE9502	B2	20
N Male	(P)	PE9503	A2	20
SMA Female	(P)	PE9656	D3	38
SMA Male	(P)	PE9654	A5	36
SMP Female		PE91055	D2	20
SMP Male		PE91048	C2	20
2.4mm In-Series:				
Female to Female		PE9453	A5	19
Female to Female	(B)	PE91459	B5	19
Female to Female	(B)	PE9640	C5	19
Female to Female	90º	PE91529	D5	19
Male to Female		PE9452	D4	19
Male to Female	90º	PE91498	E4	19
Male to Male		PE9451	C4	19
2.4mm Male To:				
1.85mm Female		PE9674	C6	19
1.85mm Male		PE9672	A6	19
1.85mm Male		PE91540	B6	19
1.85mm Male	90º	PE91157	A1	19
1.85mm Male	90º	PE91518	B1	19
2.92mm Female	90º	PE91502	E6	19
2.92mm Female		PE91451	C4	21
2.92mm Female		PE1281	D4	21
2.92mm Female		PE9454	E4	21
2.92mm Male	90º	PE91508	D6	19
2.92mm Male		PE91298	B1	21
2.92mm Male		PE9457	C1	21
3.5mm Female		PE9650	E5	22
3.5mm Male		PE91294	B4	22
3.5mm Male		PE9649	C4	22
Full Detent Mini SMP Male		PE91121	A7	19
N Female	(P)	PE9501	C7	19
N Male	(P)	PE9504	B7	19
SMA Female		PE9655	C3	38
SMA Male	(P)	PE9653	E4	36
2.4mm NMD Female To:				
2.4mm Female		PE91145	C4	20
SMA Female	(RU)	PE91146	D4	20
2.4mm NMD In-Series:				
Female to Female		PE9974	B3	20
Female to Female		PE9978	C3	20
Female to Female		PE9982	E3	20
Female to Male		PE9973	A3	20
Female to Male		PE9985	D3	20
Female to Plug		PE9984	A4	20
2.92mm Female To:				
1.85mm Female	90º	PE91163	C3	19
1.85mm Female	90º	PE91513	D3	19
1.85mm Male		PE9665	B4	21
1.85mm Male	90º	PE91527	A2	19
2.4mm Female		PE91499	A5	21
2.4mm Female		PE9456	B5	21
2.4mm Female	90º	PE91111	B1	20
2.4mm Female	90º	PE91525	C1	20
2.4mm Male		PE91451	C4	21
2.4mm Male		PE1281	D4	21
2.4mm Male		PE9454	E4	21
2.4mm Male	90º	PE91502	E6	19
2.92mm Male	(R)	PE91070	A2	21
3.5mm Female		PE9660	D5	21
3.5mm Female	90º	PE91167	E5	21
3.5mm Female	90º	PE91521	A6	21
3.5mm Male	90º	PE91520	C5	21
3.5mm Male		PE9658	A5	22
7mm Sexless	(P)	PE9461	B6	21
Full Detent Mini SMP Male		PE91127	C6	21
Mini SMP Female		PE9782	E6	21
N Female	(P)	PE9664	B7	21
N Male	(P)	PE9663	A7	21
SMA Female	(P)	PE91011	A4	38
SMA Male	(P)	PE91008	C5	36
Smooth Bore Mini SMP Male		PE91128	D6	21
SMP Female		PE91060	C7	21
SSMA Male		PE9768	D7	21
2.92mm In-Series:				
Female to Female		PE91510	C6	20
Female to Female		PE9438	D6	20
Female to Female	90º	PE91517	E6	20
Female to Female	(B) (PM)	PE9647	A7	20
Female to Female	(PM)	PE9648	B7	20
Female to Female	(PM)	PE91538	C7	20
Male to Female		PE9437	A6	20
Male to Female	90º	PE91503	B6	20
Male to Male		PE9436	D5	20
Male to Male	90º	PE91516	E5	20
2.92mm Male To:				
1.85mm Female		PE9666	A1	21
1.85mm Female	90º	PE91162	A3	19
1.85mm Female	90º	PE91512	B3	19
1.85mm Male		PE9667	E7	20
1.85mm Male	90º	PE91161	D1	19
1.85mm Male	90º	PE91519	E1	19
2.4mm Female		PE91450	D1	21
2.4mm Female		PE9455	E1	21
2.4mm Female	90º	PE91526	A1	20
2.4mm Male		PE91298	B1	21
2.4mm Male		PE9457	C1	21
2.4mm Male	90º	PE91508	D6	19
2.92mm Female	(R)	PE91070	A2	21
3.5mm Female	90º	PE91168	D2	21
3.5mm Female	90º	PE91514	E2	21
3.5mm Female		PE9659	D6	22
3.5mm Male	90º	PE91165	B2	21
3.5mm Male	90º	PE91522	C2	21
7mm Sexless		PE9460	A3	21
Mini SMP Female		PE91126	D3	21
Mini SMP Male		PE91124	B3	21
N Female	(P)	PE9662	A4	21
N Male	(P)	PE9661	E3	21
SMA Female	(P)	PE91009	E3	38
SMA Male	(P)	PE91010	B5	36
Smooth Bore Mini SMP Male		PE91125	C3	21
2.92mm NMD Female To:				
2.4mm Female		PE91144	B2	22
2.92mm NMD In-Series:				
Female to Female		PE9975	C1	22
Female to Female		PE9979	D1	22
Female to Female		PE9983	E1	22
Female to Male		PE9977	B1	22
Male to Female		PE9986	A1	22
3.5mm Female To:				
1.85mm Female		PE9748	D5	22
1.85mm Male		PE9747	B2	19
2.4mm Female		PE91291	A6	22
2.4mm Female		PE9652	B6	22
2.4mm Female		PE91547	C6	22
2.4mm Male		PE9650	E5	22
2.92mm Female		PE9660	D5	21
2.92mm Female	90º	PE91167	E5	21
2.92mm Female	90º	PE91521	A6	21
2.92mm Male		PE9659	D6	22
2.92mm Male	90º	PE91168	D2	21
2.92mm Male	90º	PE91514	E2	21
7mm Sexless	(P)	PE9325	E6	22
7mm Sexless	(P)	PE91546	A7	22
N Female	(P)	PE9323	C7	22
N Male	(P)	PE9321	B7	22
SMA Female		PE9725	C4	38
SMA Male		PE91536	E5	36
3.5mm In-Series:				
Female to Female	(B) (PM)	PE9678	B3	22
Female to Female	90º	PE91528	C3	22
Male to Female	90º	PE91523	A3	22
Male to Male	90º	PE91169	D2	22
Male to Male	90º	PE91515	E2	22
3.5mm Male To:				
1.85mm Female		PE9745	A4	22
1.85mm Male		PE9746	E3	22
2.4mm Female		PE91452	D4	22
2.4mm Female		PE9651	E4	22
2.4mm Male		PE91294	B4	22
2.4mm Male		PE9649	C4	22
2.92mm Female		PE9658	A5	22
2.92mm Female	90º	PE91520	C5	21
2.92mm Male	90º	PE91165	B2	21
2.92mm Male	90º	PE91522	C2	21
7mm Sexless	(P)	PE9326	B5	22
N Male	(P)	PE9322	C5	22
SMA Female		PE9724	B4	38
SMA Male		PE9722	D5	36
3.5mm NMD Female To:				
2.4mm Female		PE91148	E1	23
SMA Female	(RU)	PE91147	A2	23
3.5mm NMD In-Series:				
Female to Female		PE9976	A1	23
Female to Female		PE9980	B1	23
Female to Male		PE9981	E7	22
Female to Male		PE9987	C1	23
4.1/9.5 Mini DIN Female To:				
7/16 DIN Female		PE91208	D4	25
7/16 DIN Female		PE91245	E4	25
7/16 DIN Female	(LP)	PE91091	A5	25
7/16 DIN Female	(B)	PE91247	B5	25
7/16 DIN Male		PE91207	E1	25
7/16 DIN Male		PE91244	A2	25
N Female		PE91218	A6	23
N Female		PE91255	B6	23
N Female	(LP)	PE91095	C6	23
N Male		PE91219	C5	23
N Male		PE91256	D5	23
N Male	(LP)	PE91094	E5	23
4.1/9.5 Mini DIN In-Series:				
Female to Female		PE91233	D3	23
Female to Female	(B)	PE91197	E3	23
Female to Female	(B)	PE91234	A4	23

Feature: (B) Bulkhead Mount / (H) Hermetically Sealed / (I) Isolated Sealed / (LP) Low PIM / (P) Precision / (PM) Panel Mount / (PO) Push On / (QD) Quick Disconnect / (R) Radius Right Angle / (RU) Ruggedized / (SO) Snap-On

Adapter Locator

Connector Type	Feature	Model No.	C/R	Page
Male to Female		PE91195	C3	23
Male to Male		PE91194	A3	23
Male to Male		PE91231	B3	23
4.1/9.5 Mini DIN Male To:				
7/16 DIN Female		PE91209	A4	25
7/16 DIN Female		PE91246	B4	25
7/16 DIN Female	(LP)	PE91090	C4	25
7/16 DIN Male		PE91206	B1	25
7/16 DIN Male		PE91243	C1	25
7/16 DIN Male	(LP)	PE91088	D1	25
N Female		PE91217	E4	23
N Female		PE91254	A5	23
N Female	(LP)	PE91093	B5	23
N Male		PE91216	C4	23
N Male	(LP)	PE91092	D4	23
4.3-10 Female To:				
7/16 DIN Female	(LP)	PE91471	A6	25
7/16 DIN Male	(LP)	PE91469	C2	25
7/16 DIN Male	(LP)	PE91390	D2	25
N Female	(LP)	PE91475	C3	24
N Male	(LP)	PE91479	A3	24
N Male	(LP)	PE91388	C6	31
4.3-10 In-Series:				
Female to Female	(LP)	PE91464	E7	23
Female to Female	(LP)	PE91386	A1	24
Male to Female	(LP)	PE91465	B7	23
Male to Female	(LP) 90º	PE91467	C7	23
Male to Female	(LP)	PE91387	D7	23
Male to Male	(LP)	PE91466	E6	23
Male to Male	(LP)	PE91385	A7	23
4.3-10 Male To:				
7/16 DIN Female	(LP)	PE91470	C5	25
7/16 DIN Female	(LP)	PE91391	E5	25
7/16 DIN Male	(LP)	PE91468	B2	25
N Female	(LP)	PE91474	E1	24
N Female	(LP)	PE91477	A2	24
N Female	(LP) 90º	PE91483	C2	24
N Female	(LP)	PE91389	D2	24
N Male	(LP)	PE91476	C1	24
SMA Female	(LP)	PE91484	E2	24
7/16 DIN Female To:				
4.1/9.5 Mini DIN Female		PE91208	D4	25
4.1/9.5 Mini DIN Female		PE91245	E4	25
4.1/9.5 Mini DIN Female	(LP)	PE91091	A5	25
4.1/9.5 Mini DIN Female	(B)	PE91247	B5	25
4.1/9.5 Mini DIN Male		PE91209	A4	25
4.1/9.5 Mini DIN Male		PE91246	B4	25
4.1/9.5 Mini DIN Male	(LP)	PE91090	C4	25
4.3-10 Female	(LP)	PE91471	A6	25
4.3-10 Male	(LP)	PE91470	C5	25
4.3-10 Male	(LP)	PE91391	E5	25
7/16 DIN Female	(LP) (B)	PE1280	C6	25
7/16 DIN Female	(LP) (B)	PE1280	C6	25
HN Male		PE9559	D6	25
N Female		PE91213	A7	25
N Female		PE91250	B7	25
N Female	(B)	PE91215	C7	25
N Female	(B)	PE91252	D7	25
N Female	(LP)	PE9180	E7	32
N Male		PE91251	E6	25
N Male	(LP)	PE91032	E6	31
N Male		PE91134	A7	31
QD 4.3-10 Female	(LP) (QD)	PE91473	B6	25
QD 4.3-10 Male	(LP) (QD)	PE91472	D5	25
SMA Female	(LP)	PE91042	C5	38
TNC Female		PE91392	A1	45
TNC Male		PE9638	B5	44
7/16 DIN In-Series:				
Female to Female		PE91192	E5	24
Female to Female		PE91229	A6	24
Female to Female	(LP)	PE91029	B6	24
Female to Female		PE9409	C6	24
Female to Female	(B) (LP)	PE91038	E6	24
Female to Female	(B)	PE9414	A7	24
Female to Female	(B)	PE91193	B7	24
Female to Female	(B)	PE91230	C7	24
Female to Female		PE9556	D6	24
Female to Male		PE9557	D5	24
Male to Female		PE91191	D4	24
Male to Female		PE91228	E4	24
Male to Female		PE91027	A5	24
Male to Female	(LP)	PE91028	B5	24
Male to Female	90º	PE91117	C5	24
Male to Male		PE91190	A4	24
Male to Male		PE91227	B4	24
Male to Male	(LP)	PE91039	C4	24
7/16 DIN Male To:				
2.2-5 Female	(LP)	PE9799	A1	25
2.2-5 Male	(LP)	PE9798	E7	24
4.1/9.5 Mini DIN Female		PE91207	E1	25
4.1/9.5 Mini DIN Female		PE91244	A2	25
4.1/9.5 Mini DIN Male		PE91206	B1	25
4.1/9.5 Mini DIN Male		PE91243	C1	25
4.1/9.5 Mini DIN Male	(LP)	PE91088	D1	25
4.3-10 Female	(LP)	PE91469	C2	25
4.3-10 Female	(LP)	PE91390	D2	25
4.3-10 Male	(LP)	PE91468	B2	25
HN Female		PE9558	E2	25
N Female		PE91212	C3	25

Connector Type	Feature	Model No.	C/R	Page
N Female		PE91249	D3	25
N Female	(LP)	PE91031	D7	32
N Male		PE91211	A3	25
N Male		PE91248	B3	25
N Male		PE9535	D6	31
SC Female		PE91444	E3	25
SMA Female	(LP)	PE91036	A5	38
SMA Female		PE91175	B5	38
75 Ohm BNC Female To:				
75 Ohm F Female	(B)	PE91324	D2	46
75 Ohm F Female		PE9744	E5	46
75 Ohm F Male		PE9743	A5	46
75 Ohm Mini SMB Jack		PE9619	B1	47
75 Ohm Mini SMB Plug		PE9617	E7	46
75 Ohm N Female		PE9371	C5	47
75 Ohm N Male		PE9369	B3	47
75 Ohm TNC Male		PE9631	C5	48
75 Ohm BNC In-Series:				
Female to Female		PE9362	C1	46
Female to Female	(B)	PEAD1266	D1	46
Female to Female	(B)	PE9363	E1	46
Female to Female	(PM)	PE9367	A2	46
Female to Female	(B)	PE9791	B2	46
Female to Male		PE9365	B1	46
Male to Female	90º	PE9361	A1	46
Male to Male		PE9364	E7	45
75 Ohm BNC Male To:				
75 Ohm F Female		PE9741	D5	46
75 Ohm F Male		PE9742	E4	46
75 Ohm Mini SMB Jack		PE9618	A1	47
75 Ohm Mini SMB Plug		PE9616	D7	46
75 Ohm N Female		PE9368	B5	47
75 Ohm N Male		PE9370	A3	47
75 Ohm TNC Female		PE9630	A6	48
75 Ohm F Female To:				
75 Ohm BNC Female		PE9744	E5	46
75 Ohm BNC Female	(B)	PE91324	D2	46
75 Ohm BNC Male		PE9741	D5	46
75 Ohm N Female		PE9740	A6	47
75 Ohm N Male		PE9396	D3	47
75 Ohm PAL Jack		PE9634	A6	46
75 Ohm RCA Plug		PE9163	B6	46
75 Ohm TNC Female		PE91082	C6	48
75 Ohm TNC Male		PE91080	E5	48
BNC Female		PE9153	D3	27
BNC Male		PE9150	D1	27
N Male		PE9155	B2	32
SMA Female		PE91002	A7	38
SMA Male		PE91003	A7	36
UHF Female		PE9167	B7	45
UHF Male		PE9165	B6	45
75 Ohm F In-Series:				
Female to Female	(P)	PE91349	E3	46
Female to Female		PE9164	A4	46
Female to Female	(B)	PEAD1265	B4	46
Female to Female	(B) (PM)	PE9734	C4	46
Male to Female	(PO)	PE9160	C3	46
Male to Female		PE9759	D3	46
Male to Male	(P)	PE91348	A3	46
Male to Male		PE9760	B3	46
75 Ohm F Male To:				
75 Ohm BNC Female		PE9743	A5	46
75 Ohm BNC Male		PE9742	E4	46
75 Ohm N Female		PE9397	D5	47
75 Ohm N Female		PE9739	E5	47
75 Ohm N Male		PE9738	C3	47
75 Ohm PAL Jack		PE9632	C5	46
75 Ohm PAL Plug		PE9633	B5	46
75 Ohm TNC Female		PE91083	B6	48
75 Ohm TNC Male		PE91081	D5	48
BNC Female		PE9151	C3	27
BNC Male		PE9152	C1	27
N Female		PE9389	B3	33
SMA Female		PE91045	E6	38
75 Ohm Mini SMB In-Series:				
Jack to Jack		PE9608	A7	46
Jack to Jack	(B)	PE9611	B7	46
Plug to Jack		PE9610	E6	46
Plug to Plug		PE9609	D6	46
75 Ohm Mini SMB Jack To:				
75 Ohm BNC Female		PE9619	B1	47
75 Ohm BNC Male		PE9618	A1	47
75 Ohm N Female		PE9615	C6	47
75 Ohm N Male		PE9614	A4	47
75 Ohm SMB Plug		PE9736	C2	48
75 Ohm Mini SMB Plug To:				
75 Ohm BNC Female		PE9617	E7	46
75 Ohm BNC Male		PE9616	D7	46
75 Ohm N Female		PE9613	B6	47
75 Ohm N Male		PE9612	E3	47
75 Ohm SMB Jack		PE9735	E2	48
75 Ohm N Female To:				
75 Ohm BNC Female		PE9371	C5	47
75 Ohm BNC Male		PE9368	B5	47
75 Ohm F Female		PE9740	A6	47
75 Ohm F Male		PE9397	D5	47
75 Ohm F Male		PE9739	E5	47
75 Ohm Mini SMB Jack		PE9615	C6	47

Connector Type	Feature	Model No.	C/R	Page
75 Ohm Mini SMB Plug		PE9613	B6	47
75 Ohm SMB Jack		PE9583	E6	47
75 Ohm SMB Plug		PE9585	D6	47
75 Ohm SMC Jack		PE9587	B7	47
75 Ohm SMC Plug		PE9589	A7	47
75 Ohm TNC Female		PE9629	D7	47
75 Ohm TNC Male		PE9628	C7	47
75 Ohm N In-Series:				
Female to Female		PE9306	B2	47
Female to Female	(B) (PM)	PE9417	C2	47
Female to Female	(B)	PE9416	D2	47
Male to Female		PE9391	E1	47
Male to Female	90º	PE9307	A2	47
Male to Male		PE9308	D1	47
75 Ohm N Male To:				
75 Ohm BNC Female		PE9369	B3	47
75 Ohm BNC Male		PE9370	A3	47
75 Ohm F Female		PE9396	D3	47
75 Ohm F Male		PE9738	C3	47
75 Ohm Mini SMB Jack		PE9614	A4	47
75 Ohm Mini SMB Plug		PE9612	E3	47
75 Ohm SMB Jack		PE9582	C4	47
75 Ohm SMB Plug		PE9584	B4	47
75 Ohm SMC Jack		PE9586	D4	47
75 Ohm TNC Female		PE9627	A5	47
75 Ohm TNC Male		PE9626	E4	47
75 Ohm PAL In-Series:				
Plug to Plug		PE9680	A1	48
75 Ohm PAL Jack To:				
75 Ohm F Female		PE9634	A6	46
75 Ohm F Male		PE9632	C5	46
75 Ohm PAL Plug To:				
75 Ohm F Male		PE9633	B5	46
75 Ohm Push-On RCA Jack To:				
BNC Male	(PO)	PE9171	A2	27
75 Ohm RCA Jack To:				
BNC Female		PE9015	A4	27
75 Ohm RCA Plug To:				
75 Ohm F Female		PE9163	B6	46
BNC Female		PE9158	E3	27
75 Ohm SMB In-Series:				
Jack to Jack		PE9248	A2	48
Jack to Plug		PE9245	D1	48
Plug to Plug		PE9271	C1	48
75 Ohm SMB Jack To:				
75 Ohm Mini SMB Plug		PE9735	E2	48
75 Ohm N Female		PE9583	E6	47
75 Ohm N Male		PE9582	C4	47
BNC Female		PE9231	B4	27
BNC Male		PE9229	D2	48
75 Ohm SMB Plug To:				
75 Ohm Mini SMB Jack		PE9736	C2	48
75 Ohm N Female		PE9585	D6	47
75 Ohm N Male		PE9584	B4	47
BNC Female		PE9232	B2	48
BNC Male		PE9230	B2	27
75 Ohm SMC In-Series:				
Jack to Jack		PE9227	C3	48
Jack to Jack	(B) (PM)	PE9228	D3	48
Jack to Plug		PE9244	B3	48
75 Ohm SMC Jack To:				
75 Ohm N Female		PE9587	B7	47
75 Ohm N Male		PE9586	D4	47
BNC Female		PE9235	A4	48
BNC Male		PE91044	D2	27
75 Ohm SMC Plug To:				
75 Ohm N Female		PE9589	A7	47
BNC Female		PE9236	C4	27
BNC Male		PE9234	C2	27
75 Ohm TNC Female To:				
75 Ohm BNC Male		PE9630	A6	48
75 Ohm F Female		PE91082	C6	48
75 Ohm F Male		PE91083	B6	48
75 Ohm N Female		PE9629	D7	47
75 Ohm N Male		PE9627	A5	47
75 Ohm TNC In-Series:				
Female to Female		PE9622	D4	48
Female to Female	(B) (PM)	PE9625	E4	48
Female to Female	(B)	PE9624	A5	48
Male to Female	90º	PE9623	C4	48
75 Ohm TNC Male To:				
75 Ohm BNC Female		PE9631	C5	48
75 Ohm F Female		PE91080	E5	48
75 Ohm F Male		PE91081	D5	48
75 Ohm N Female		PE9628	C7	47
75 Ohm N Male		PE9626	E4	47
78 Ohm BNC Twinax In-Series:				
Jack to Jack		PE9378	C7	48
Jack to Jack	(B)	PE9280	D7	48
Jack to Plug		PE9375	B7	48
Plug to Jack	90º	PE9377	A7	48
Plug to Plug		PE9376	E6	48
7mm Sexless To:				
2.92mm Female	(P)	PE9461	B6	21
2.92mm Male		PE9460	A3	21
3.5mm Female	(P)	PE9325	E6	22
3.5mm Female	(P)	PE91546	A7	22

Feature: (B) Bulkhead Mount / (H) Hermetically Sealed / (I) Isolated Sealed / (LP) Low PIM / (P) Precision / (PM) Panel Mount / (PO) Push On / (QD) Quick Disconnect / (R) Radius Right Angle / (RU) Ruggedized / (SO) Snap-On

Adapter Locator

Connector Type	Feature	Model No.	C/R	Page
3.5mm Male	(P)	PE9326	B5	22
BNC Female	(P)	PE9220	D2	23
BNC Male	(P)	PE9221	C2	23
N Female	(P)	PE9216	C7	32
N Male	(P)	PE9217	B6	31
SMA Female	(P)	PE9214	D4	38
SMA Female	(P) (PM)	PE9327	E4	38
SMA Male	(P)	PE9215	A6	36
TNC Female	(P)	PE9218	E7	44
TNC Male	(P)	PE9219	A5	44
95 Ohm 3/4"-20 Twinax In-Series:				
Female to Female		PE9199	B1	49
Female to Female	(B)	PE9373	C1	49
Female to Male		PE9374	A1	49
Banana Binding Post Jack To:				
BNC Male		PE9169	E2	49
Banana Plug To:				
BNC Female		PE9175	E1	49
BMA In-Series:				
Jack to Jack		PE91395	A3	26
BNC Female To:				
10-32 Female		PE9752	C2	26
10-32 Female	(B)	PE9754	D2	26
10-32 Male		PE9753	E1	26
10-32 Male	(B)	PE9755	A2	26
75 Ohm F Female		PE9153	D3	27
75 Ohm F Male		PE9151	C3	27
75 Ohm RCA Jack		PE9015	A4	27
75 Ohm RCA Plug		PE9158	E3	27
75 Ohm SMB Jack		PE9231	B4	27
75 Ohm SMB Plug		PE9232	B2	48
75 Ohm SMC Jack		PE9235	A4	48
75 Ohm SMC Plug		PE9236	C4	27
7mm Sexless	(P)	PE9220	D2	23
Banana Plug		PE9175	E1	49
C Female		PE9537	A3	27
C Female	(B) (PM)	PE9204	B3	27
C Male		PE9087	E2	27
Double Banana Binding Post Jack		PE9013	B3	49
Double Banana Plug		PE9008	C2	49
FME Jack		PE9712	D1	28
HN Male		PE9126	C5	28
MCX Jack		PE9466	A3	29
MCX Jack	(B) (PM)	PE9520	B3	29
MCX Plug		PE9467	D2	29
Mini UHF Male		PE9342	C7	29
MMCX Jack		PE9516	C3	30
N Female		PE9206	E1	33
N Female	(P)	PE9492	A2	33
N Female	(B) (PM)	PE9261	B2	33
N Female	(PM)	PE9238	C2	33
N Female	(B) (PM)	PE9540	D2	33
N Male		PE9002	E7	31
N Male	(P)	PE9491	A1	32
N Male	90º	PE9278	B1	32
N Male	(PM)	PE9388	C1	32
SC Female		PE9571	E6	34
SMA Female		PE9075	A6	38
SMA Female		PE9496	B6	38
SMA Female	(B)	PE9185	C6	38
SMA Female	(B)	PE9407	D6	38
SMA Male		PE9074	D6	36
SMA Male		PE9495	E6	36
SMB Jack		PE9136	C2	42
SMB Jack	(B)	PE9240	D2	42
SMB Plug		PE9137	E1	42
SMB Plug	(B) (PM)	PE9241	A2	42
SMC Jack		PE9140	D5	42
SMC Jack	(B)	PE9108	E5	42
SMC Plug		PE9141	E4	42
SSMA Male		PE91046	D3	43
SSMB Jack		PE9394	B5	43
SSMB Plug		PE9395	A5	43
TNC Female		PE9097	C1	45
TNC Male		PE9088	C5	44
TNC Male	90º	PE9783	D5	44
UHF Female		PE9421	A7	45
UHF Male		PE91328	A6	45
BNC In-Series:				
Female to Female		PE9084	B6	26
Female to Female		PE9003	C6	26
Female to Female	(B) (PM)	PE9420	D6	26
Female to Female	(B)	PE9093	E6	26
Female to Female	(B)	PE9172	A7	26
Female to Female	(PM)	PE9106	B7	26
Female to Male		PE9001	A6	26
Female to Male		PE9529	A5	27
Male to Female		PE9269	B5	26
Male to Female	90º	PE9085	C5	26
Male to Female		PE9174	D5	26
Male to Female		PE9484	E5	26
Male to Female		PE9530	E4	27
Male to Male		PE9000	E4	26
Male to Male	90º	PE9758	A5	26
BNC Male To:				
10-32 Female		PE9750	B2	26
10-32 Male		PE9751	D1	26
75 Ohm F Female		PE9150	D1	27
75 Ohm F Male		PE9152	C1	27
75 Ohm Push-On RCA Jack	(PO)	PE9171	A2	27
75 Ohm SMB Jack		PE9229	D2	48
75 Ohm SMB Plug		PE9230	B2	27
75 Ohm SMC Jack		PE91044	D2	27
75 Ohm SMC Plug		PE9234	C2	27
7mm Sexless	(P)	PE9221	C2	23
Banana Binding Post Jack		PE9169	E2	49
BNC Triax Female		PE91104	E7	26
C Female		PE9109	B1	27
C Male		PE9536	A1	27
Double Banana Binding Post Jack		PE9011	D7	26
Double Banana Plug		PE9009	B2	49
FME Jack		PE9711	C1	28
FME Plug		PE9697	A1	28
FME Plug	90º	PE9698	B1	28
GR874 Sexless		PE9223	D2	28
HN Female		PE9129	C6	28
HN Male		PE9567	B5	28
MCX Jack		PE9468	E2	29
MCX Plug		PE9469	C2	29
MHV Female		PE9406	E1	27
Mini UHF Female		PE9341	B1	30
MMCX Jack		PE9518	B3	30
MMCX Plug		PE9517	D2	30
N Female		PE9005	A1	33
N Female	(P)	PE9490	B1	33
N Female	90º	PE9566	C1	33
N Female	(PM)	PE9123	D1	33
N Male		PE9127	B7	31
N Male	(P)	PE9489	C7	31
N Male	90º	PE9565	D7	31
Rev. Pol. TNC Female		PE91087	C4	45
SC Male		PE9568	D6	34
SMA Female		PE9073	D5	38
SMA Female		PE9494	E5	38
SMA Male		PE9072	B6	36
SMA Male		PE9493	C6	36
SMB Jack		PE9132	B2	42
SMB Plug		PE9135	D1	42
SMC Jack		PE9138	C5	42
SMC Plug		PE9139	D4	42
SSMA Female		PE9191	A4	43
SSMA Male		PE9213	C3	43
SSMB Plug		PE9393	E4	43
TNC Female		PE9098	B1	45
UHF Female		PE91329	E6	45
UHF Male		PE9201	E5	45
BNC Triax Female To:				
BNC Male		PE91104	E7	26
BNC Triax In-Series:				
Female to Female		PE91107	E3	49
Female to Female	(B) (PM)	PE91105	A4	49
Male to Female		PE91106	D3	49
C Female To:				
BNC Female		PE9537	A3	27
BNC Female	(B) (PM)	PE9204	B3	27
BNC Male		PE9109	B1	27
GR874 Sexless		PE9301	E2	28
HN Male		PE9296	E5	28
N Female		PE9539	A3	33
N Male		PE91446	E1	32
N Male	90º	PE9239	A2	32
TNC Male		PE9562	E5	44
C In-Series:				
C Female to C Female		PE9208	A6	27
C Female to C Female		PE9294	B6	27
C Female to C Female	(B) (PM)	PE9186	C6	27
C Female to C Male		PE9207	E5	27
C Male to C Female	90º	PE9293	D5	27
C Male to C Male		PE9300	C5	27
C Male To:				
BNC Female		PE9087	E2	27
BNC Male		PE9536	A1	27
HN Female		PE9212	D6	28
HN Male		PE9579	D5	28
N Female		PE9295	E2	33
N Male		PE9538	D1	32
TNC Female		PE9564	D1	45
Double Banana Binding Post Jack To:				
BNC Female		PE9013	B3	49
BNC Male		PE9011	D7	26
Double Banana Plug To:				
BNC Female		PE9008	C2	49
BNC Male		PE9009	B2	49
D-Sub In-Series:				
Plug to Plug		PE9688	E6	27
Plug to Receptacle		PE9687	A7	27
Receptacle to Receptacle		PE9689	B7	27
FME In-Series:				
Plug to Plug		PE9696	D7	27
FME Jack To:				
BNC Female		PE9712	D1	28
BNC Male		PE9711	C1	28
Mini UHF Female		PE9710	C1	30
Mini UHF Male		PE9709	A1	30
SMA Female		PE9708	C7	38
SMA Male		PE9707	B7	36
TNC Female		PE9714	E1	45
TNC Male		PE9713	C6	44
FME Plug To:				
BNC Male		PE9697	A1	28
BNC Male	90º	PE9698	B1	28
Mini UHF Male		PE9705	D7	29
Mini UHF Male	90º	PE9706	E7	29
N Male		PE9704	C2	32
SMA Female		PE9703	B7	38
TNC Male		PE9699	A6	44
TNC Male	90º	PE9700	B6	44
UHF Male		PE9701	C6	45
Full Detent Mini SMP Male To:				
2.4mm Female		PE91122	D1	20
2.4mm Male		PE91121	A7	19
2.92mm Female		PE91127	C6	21
SMA Female		PE91299	D1	39
SMA Female		PE91129	A2	39
SMA Male		PE91302	C1	37
SMA Male	(P)	PE91052	E1	37
Full Detent SMP Male To:				
SMA Female		PE91305	A7	39
SMA Female	(P)	PE91056	E7	39
SMA Female	(B) (PM)	PE91054	C1	40
SMA Female	(P) (PM)	PE91058	E1	40
SMA Male		PE91309	A6	37
SMA Male	(P)	PE91063	D6	37
GR874 Sexless In-Series:				
Sexless to Sexless	90º	PE9286	A2	28
Sexless to Sexless		PE9285	B2	28
GR874 Sexless To:				
BNC Male		PE9223	D2	28
C Female		PE9301	E2	28
HN Female		PE9387	E6	28
HN Male		PE9386	A6	28
N Female		PE9258	C3	33
N Male		PE9257	D2	32
SMA Female		PE9260	D7	38
SMA Male		PE9259	C7	36
HN Female To:				
7/16 DIN Male		PE9558	E2	25
BNC Male		PE9129	C6	28
C Male		PE9212	D6	28
GR874 Sexless		PE9387	E6	28
LC Male		PE9181	A1	29
N Female		PE9360	E3	33
N Female	(PM)	PE9553	A4	33
N Male		PE9125	A3	32
SMA Female		PE9255	A1	39
SMA Male		PE9256	E7	36
HN In-Series:				
Female to Female		PE9580	C4	28
Female to Female		PE9574	D4	28
Female to Female	(B) (PM)	PE9193	E4	28
Female to Male		PE9575	B4	28
Male to Female		PE9576	D3	28
Male to Female	90º	PE9205	E3	28
Male to Female		PE9578	A4	28
Male to Male		PE9210	B3	28
Male to Male	90º	PE9577	C3	28
HN Male To:				
7/16 DIN Female		PE9559	D6	25
BNC Female		PE9126	C5	28
BNC Male		PE9567	B5	28
C Female		PE9296	E5	28
C Male		PE9579	D5	28
GR874 Sexless		PE9386	A6	28
LC Female		PE9413	B1	29
MHV Female		PE9264	B6	28
N Female		PE9194	D3	33
N Male		PE9554	E2	32
SMA Female		PE9253	E7	38
SMA Male		PE91448	D7	36
TNC Male		PE9563	D6	44
LC Female To:				
HN Male		PE9413	B1	29
N Female		PE9298	C4	33
N Male		PE9299	B3	32
LC In-Series:				
Female to Female		PE9419	D7	28
Male to Female	90º	PE9398	C7	28
Male to Male		PE9569	B7	28
LC Male To:				
HN Female		PE9181	A1	29
N Female		PE9237	B4	33
Limited Detent SMP Male To:				
SMA Female		PE91306	B7	39
SMA Female	(P)	PE91050	D7	39
SMA Female	(P)	PE9512	A1	40
SMA Female		PE9778	B1	40
SMA Female	(P) (PM)	PE91066	B2	40
SMA Male		PE91310	B6	37
SMA Male	(P)	PE9511	E6	37
TNC Female	(B)	PE91073	E2	45
MCX In-Series:				
Jack to Jack		PE9524	E1	29
Jack to Jack	(B)	PE9474	A2	29

Feature: (B) Bulkhead Mount / (H) Hermetically Sealed / (I) Isolated Sealed / (LP) Low PIM / (P) Precision / (PM) Panel Mount / (PO) Push On / (QD) Quick Disconnect / (R) Radius Right Angle / (RU) Ruggedized / (SO) Snap-On

Adapter Locator

Connector Type	Feature	Model No.	C/R	Page
Plug to Jack		PE9479	D1	29
MCX Jack To:				
BNC Female		PE9466	A3	29
BNC Female	(B) (PM)	PE9520	B3	29
BNC Male		PE9468	E2	29
MMCX Jack		PE9526	E3	30
MMCX Plug		PE9525	A3	30
N Female		PE9462	E4	33
N Male		PE9464	D3	32
SMA Female		PE9470	C1	39
SMA Male		PE9472	B1	37
TNC Female		PE9544	B2	45
TNC Female	(B) (PM)	PE9521	C2	45
TNC Male		PE9542	A7	44
MCX Plug To:				
BNC Female		PE9467	D2	29
BNC Male		PE9469	C2	29
MMCX Jack		PE9528	D3	30
MMCX Plug		PE9527	E2	30
N Female		PE9463	D4	33
N Male		PE9465	C3	32
SMA Female		PE9471	B1	39
SMA Male		PE9473	A1	37
TNC Female		PE9545	A2	45
TNC Male		PE9543	E6	44
MHV Female To:				
BNC Male		PE9406	E1	27
HN Male		PE9264	B6	28
SHV Jack		PE9339	C5	29
SHV Plug		PE9265	B5	29
MHV In-Series:				
Female to Female		PE9267	B4	29
Female to Female	(B)	PE9268	C4	29
Female to Male		PE9211	A4	29
Male to Female		PE9297	D3	29
Male to Female	90º	PE9266	E3	29
MHV Male To:				
SHV Jack		PE9335	A5	29
SHV Plug		PE9340	E4	29
Mini SMP Female To:				
2.4mm Female		PE91123	E1	20
2.92mm Female		PE9782	E6	21
2.92mm Male		PE91126	D3	21
SMA Female		PE91301	B2	39
SMA Female	(P)	PE91051	C2	39
SMA Male		PE91304	A2	37
SMA Male	(P)	PE91103	B2	37
Mini SMP In-Series:				
Female to Female		PE9780	E5	29
Female to Female		PE91069	A6	29
Mini SMP Male To:				
2.92mm Male		PE91124	B3	21
Mini UHF Female To:				
BNC Male		PE9341	B1	30
FME Jack		PE9710	C1	30
N Male		PE9064	E3	32
TNC Male		PE9345	B7	44
UHF Male		PE9348	D6	45
Mini UHF In-Series:				
Female to Female		PE9343	E6	29
Female to Female		PE9066	B7	29
Female to Male		PE9065	D6	29
Male to Female	90º	PE9347	C6	29
Mini UHF Male To:				
BNC Female		PE9342	C7	29
FME Jack		PE9709	A1	30
FME Plug		PE9705	D7	29
FME Plug	90º	PE9706	E7	29
N Female		PE9183	A5	33
TNC Female		PE9346	D2	45
UHF Female		PE91447	C7	45
MMBX In-Series:				
Plug to Plug	(SO)	PE91370	B4	30
Plug to Plug		PE91371	C4	30
Plug to Plug	(SO)	PE91372	D4	30
Plug to Plug	(SO)	PE91373	E4	30
MMCX In-Series:				
Jack to Jack		PE9523	A2	30
Jack to Jack	(B) (PM)	PE9522	B2	30
Plug to Jack		PE9480	E1	30
MMCX Jack To:				
BNC Female		PE9516	C3	30
BNC Male		PE9518	B3	30
MCX Jack		PE9526	E3	30
MCX Plug		PE9528	D3	30
SMA Female		PE9477	B3	39
SMA Male		PE9478	A3	37
MMCX Plug To:				
BNC Male		PE9517	D2	30
MCX Jack		PE9525	A3	30
MCX Plug		PE9527	E2	30
SMA Female		PE9475	A3	39
SMA Male		PE9476	E2	37
N Female To:				
1.85mm Female		PE9721	A4	19
1.85mm Male		PE9719	D2	19
2.2-5 Female	(LP)	PE9795	E1	34
2.2-5 Male	(LP)	PE9794	D1	34
2.4mm Female	(P)	PE9502	B2	20
2.4mm Male	(P)	PE9501	C7	19
2.92mm Female	(P)	PE9664	B7	21
2.92mm Male	(P)	PE9662	A4	21
3.5mm Female	(P)	PE9323	C7	22
4.1/9.5 Mini DIN Female		PE91218	A6	23
4.1/9.5 Mini DIN Female		PE91255	B6	23
4.1/9.5 Mini DIN Female	(LP)	PE91095	C6	23
4.1/9.5 Mini DIN Male		PE91217	E4	23
4.1/9.5 Mini DIN Male		PE91254	A5	23
4.1/9.5 Mini DIN Male	(LP)	PE91093	B5	23
4.3-10 Female	(LP)	PE91475	C3	24
4.3-10 Male	(LP)	PE91474	E1	24
4.3-10 Male	(LP)	PE91477	A2	24
4.3-10 Male	(LP) 90º	PE91483	C2	24
4.3-10 Male	(LP)	PE91389	D2	24
7/16 DIN Female	(LP)	PE9180	E7	32
7/16 DIN Female		PE91213	A7	25
7/16 DIN Female		PE91250	B7	25
7/16 DIN Female	(B)	PE91215	C7	25
7/16 DIN Female	(B)	PE91252	D7	25
7/16 DIN Male	(LP)	PE91031	D7	32
7/16 DIN Male		PE91212	C3	25
7/16 DIN Male		PE91249	D3	25
75 Ohm F Male		PE9389	B3	33
7mm Sexless	(P)	PE9216	C7	32
BNC Female		PE9206	E1	33
BNC Female	(P)	PE9492	A2	33
BNC Female	(B) (PM)	PE9261	B2	33
BNC Female	(PM)	PE9238	C2	33
BNC Female	(B) (PM)	PE9540	D2	33
BNC Male		PE9005	A1	33
BNC Male	(P)	PE9490	B1	33
BNC Male	90º	PE9566	C1	33
BNC Male	(PM)	PE9123	D1	33
C Female		PE9539	A3	33
C Male		PE9295	E2	33
GR874 Sexless		PE9258	C3	33
HN Female		PE9360	E3	33
HN Female	(PM)	PE9553	A4	33
HN Male		PE9194	D3	33
LC Female		PE9298	C4	33
LC Male		PE9237	B4	33
MCX Jack		PE9462	E4	33
MCX Plug		PE9463	D4	33
Mini UHF Male		PE9183	A5	33
QD 4.3-10 Female	(LP) (QD)	PE91482	D3	24
QD 4.3-10 Male	(LP) (QD)	PE91478	B2	24
Rev. Pol. SMA Male		PE9732	A4	41
Rev. Pol. TNC Male		PE9731	B3	34
SC Female		PE9292	C5	33
SC Male		PE9277	B5	33
SMA Female		PE9083	C4	39
SMA Female	(P)	PE9432	D4	39
SMA Female	(B)	PE9252	E4	39
SMA Female	(B) (P)	PE9486	A5	39
SMA Female	(PM)	PE9104	B5	39
SMA Female	(P) (PM)	PE9434	C5	39
SMA Female	(B)	PE9408	D5	39
SMA Female	(B) (P) (PM)	PE9435	E5	39
SMA Male	(LP)	PE91178	D5	33
SMA Male		PE9082	E3	37
SMA Male	(P)	PE9433	A4	37
SMA Male	(B) (P)	PE9487	B4	37
SMA Male	(PM)	PE9105	C4	37
SMA Male	(P) (PM)	PE9497	D4	37
SMA Male	(B) (P)	PE9488	E4	37
SMB Jack		PE9315	A6	33
SMB Plug		PE9316	E5	33
SMC Jack		PE9319	C6	33
SMC Plug		PE9320	B6	33
SSMA Female		PE9354	C4	43
TNC Female		PE9131	B7	33
TNC Female	(P)	PE9449	C7	33
TNC Female	(PM)	PE9552	D7	33
TNC Female	(B)	PE9482	E7	33
TNC Female	(P) (PM)	PE9450	A1	34
TNC Male		PE9089	D6	33
TNC Male	(P)	PE91506	E6	33
TNC Male	90º	PE9263	A7	33
UHF Female		PE9385	C1	34
UHF Male		PE9112	B1	34
N In-Series:				
Female to Female		PE91200	B2	31
Female to Female		PE91237	C2	31
Female to Female		PE9006	D2	31
Female to Female	(LP)	PE91140	E2	31
Female to Female		PE91141	A3	31
Female to Female	(P)	PE91530	B3	31
Female to Female	90º	PE9359	C3	31
Female to Female		PE9101	D3	31
Female to Female		PE9548	E3	31
Female to Female	(B)	PE9128	A4	31
Female to Female	(B)	PE9383	B4	31
Female to Female	(B) 90º	PE9541	C4	31
Female to Female	(PM)	PE9173	D4	31
Female to Female	(P) (PM)	PE9429	E4	31
Female to Female	(B)	PE91201	A5	31
Female to Female	(B)	PE91238	B5	31
Female to Female	(B) (LP)	PE91179	C5	31
Female to Female	(B) (P)	PE9500	D5	31
Female to Female	(B)	PE9382	E5	31
Female to Male		PE9350	E1	31
Female to Male		PE9102	A2	31
Female to Male		PE9770	C2	34
Male to Female		PE91199	C6	30
Male to Female		PE91236	D6	30
Male to Female	(LP)	PE91040	E6	30
Male to Female	(PO)	PE91114	A7	30
Male to Female	(P)	PE91531	B7	30
Male to Female		PE9311	C7	30
Male to Female		PE9349	D7	30
Male to Female	(QD)	PE9547	E7	30
Male to Female	(P) (R)	PE91350	A1	31
Male to Female	90º	PE9086	B1	31
Male to Female		PE9481	C1	31
Male to Female	(B)	PE9595	D1	31
Male to Female		PE9771	B2	34
Male to Male		PE91198	B5	30
Male to Male		PE9007	C5	30
Male to Male	(LP)	PE91034	D5	30
Male to Male	(P)	PE91532	E5	30
Male to Male	90º	PE9198	A6	30
Male to Male		PE9390	B6	30
N Male To:				
1.85mm Female		PE9720	E3	19
1.85mm Male		PE9718	C2	19
2.2-5 Female	(LP)	PE9797	B7	32
2.2-5 Male	(LP)	PE9796	A7	32
2.4mm Female	(P)	PE9503	A2	20
2.4mm Male	(P)	PE9504	B7	19
2.92mm Female	(P)	PE9663	A7	21
2.92mm Male	(P)	PE9661	E3	21
3.5mm Female	(P)	PE9321	B7	22
3.5mm Male	(P)	PE9322	C5	22
4.1/9.5 Mini DIN Female		PE91219	C5	23
4.1/9.5 Mini DIN Female		PE91256	D5	23
4.1/9.5 Mini DIN Female	(LP)	PE91094	E5	23
4.1/9.5 Mini DIN Male		PE91216	C4	23
4.1/9.5 Mini DIN Male	(LP)	PE91092	D4	23
4.3-10 Female	(LP)	PE91388	C6	31
4.3-10 Female	(LP)	PE91479	A3	24
4.3-10 Male	(LP)	PE91476	C1	24
7/16 DIN Female	(LP)	PE91032	E6	31
7/16 DIN Female		PE91134	A7	31
7/16 DIN Female		PE91251	E6	25
7/16 DIN Male		PE9535	D6	31
7/16 DIN Male		PE91211	A3	25
7/16 DIN Male		PE91248	B3	25
75 Ohm F Female		PE9155	B2	32
7mm Sexless	(P)	PE9217	B6	31
BNC Female		PE9002	E7	31
BNC Female	(P)	PE9491	A1	32
BNC Female	90º	PE9278	B1	32
BNC Female	(PM)	PE9388	C1	32
BNC Male		PE9127	B7	31
BNC Male	(P)	PE9489	C7	31
BNC Male	90º	PE9565	D7	31
C Female		PE91446	E1	32
C Female	90º	PE9239	A2	32
C Male		PE9538	D1	32
FME Plug		PE9704	C2	32
GR874 Sexless		PE9257	D2	32
HN Female		PE9125	A3	32
HN Male		PE9554	E2	32
LC Female		PE9299	B3	32
MCX Jack		PE9464	D3	32
MCX Plug		PE9465	C3	32
Mini UHF Female		PE9064	E3	32
QD 4.3-10 Female	(LP) (QD)	PE91481	B3	24
QD 4.3-10 Male	(LP) (QD)	PE91480	D1	24
Rev. Pol. SMA Female		PE9733	D4	41
Rev. Pol. TNC Female		PE9730	A3	34
SC Female		PE9196	B4	32
SC Male		PE9570	A4	32
SMA Female	(LP)	PE91177	C4	32
SMA Female	(P)	PE91339	D4	32
SMA Female		PE9081	C3	39
SMA Female	(B)	PE9551	E3	39
SMA Female	(PM)	PE9275	A4	39
SMA Female	(P) (PM)	PE9498	B4	39
SMA Male		PE9080	B3	37
SMA Male	(P)	PE9431	C3	37
SMA Male	(P) (PM)	PE9499	D3	37
SMB Jack		PE9313	A5	32
SMB Plug		PE9314	E4	32
SMC Jack		PE9317	C5	32
SMC Plug		PE9318	B5	32
SSMA Female		PE9352	B4	43
SSMA Male		PE9351	E3	43
TNC Female		PE9090	A6	32
TNC Female	90º	PE9550	B6	32
TNC Female		PE91537	C6	32
TNC Male		PE9130	D5	32
TNC Male	(P)	PE9446	E5	32
UHF Female		PE9111	E6	32
UHF Male		PE9113	D6	32
Push-On SMA Male To:				
SMA Female	(PO)	PE91336	A5	37

Feature: (B) Bulkhead Mount / (H) Hermetically Sealed / (I) Isolated Sealed / (LP) Low PIM / (P) Precision / (PM) Panel Mount / (PO) Push On / (QD) Quick Disconnect / (R) Radius Right Angle / (RU) Ruggedized / (SO) Snap-On

Adapter Locator

Connector Type	Feature	Model No.	C/R	Page
Push-On SMP Female To:				
Snap-On MMBX Plug	(PO) (SO)	PE91364	C1	43
QD 4.3-10 Female To:				
7/16 DIN Female	(LP) (QD)	PE91473	B6	25
N Female	(LP) (QD)	PE91482	D3	24
N Male	(LP) (QD)	PE91481	B3	24
QD 4.3-10 Male To:				
7/16 DIN Female	(LP) (QD)	PE91472	D5	25
N Female	(LP) (QD)	PE91478	B2	24
N Male	(LP) (QD)	PE91480	D1	24
QD N Male To:				
SMA Female	(QD)	PE9684	D3	39
QMA In-Series:				
Female to Female	(SO)	PE91343	A4	34
Male to Female	(SO)	PE91342	E3	34
Male to Male	(SO)	PE91341	D3	34
QMA Male To:				
SMA Female		PE9786	A6	39
Reverse Polarity MCX Plug To:				
SMA Male		PE9581	B3	41
Reverse Polarity N In-Series:				
Female to Female		PE9773	D2	34
Reverse Polarity SMA Female To:				
N Male		PE9733	D4	41
Rev. Pol. TNC Female		PE9606	E5	41
Rev. Pol. TNC Male		PE9607	D5	41
TNC Female		PE9599	A5	41
TNC Male		PE9598	E4	41
Reverse Polarity SMA In-Series:				
Female to Female		PE91262	A2	41
Female to Female		PE91334	B2	41
Female to Female	(B) (PM)	PE9593	C2	41
Female to Female	(PM)	PE91270	D2	41
Female to Female	(PM)	PE91269	E2	41
Male to Female	(QD)	PE91267	D7	40
Male to Female	90º	PE91263	E7	40
Male to Female	(QD)	PE91268	C1	41
Male to Female		PE91331	D1	41
Male to Female	90º	PE9594	E1	41
Male to Male	(QD)	PE91266	C7	40
Male to Male		PE91261	A1	41
Male to Male		PE91330	B1	41
Reverse Polarity SMA Male To:				
N Female		PE9732	A4	41
Rev. Pol. TNC Female		PE9604	C5	41
Rev. Pol. TNC Male		PE9605	B5	41
TNC Female		PE9596	C4	41
TNC Male		PE9597	B4	41
Reverse Polarity TNC Female To:				
BNC Male		PE91087	C4	45
N Male		PE9730	A3	34
Rev. Pol. SMA Female		PE9606	E5	41
Rev. Pol. SMA Male		PE9604	C5	41
SMA Female		PE9603	E3	41
SMA Male		PE9600	C3	41
Reverse Polarity TNC In-Series:				
Male to Female	90º	PE9918	B4	45
Reverse Polarity TNC Male To:				
N Female		PE9731	B3	34
Rev. Pol. SMA Female		PE9607	D5	41
Rev. Pol. SMA Male		PE9605	B5	41
SMA Female		PE9602	D3	41
SC Female To:				
7/16 DIN Male		PE91444	E3	25
BNC Female		PE9571	E6	34
N Female		PE9292	C5	33
N Male		PE9196	B4	32
SC In-Series:				
Female to Female		PE9404	A6	34
Female to Female	(B)	PE9573	B6	34
Female to Male		PE9225	E5	34
Male to Female	90º	PE9405	D5	34
Male to Male		PE9403	C5	34
SC Male To:				
BNC Male		PE9568	D6	34
N Female		PE9277	B5	33
N Male		PE9570	A4	32
SHV In-Series:				
Jack to Jack		PE9337	E7	34
Jack to Jack	(B)	PE9336	A1	35
Jack to Plug		PE9249	D7	34
Plug to Jack		PE9749	B7	34
Plug to Jack	90º	PE9338	C7	34
SHV Jack To:				
MHV Female		PE9339	C5	29
MHV Male		PE9335	A5	29
SHV Plug To:				
MHV Female		PE9265	B5	29
MHV Male		PE9340	E4	29
Slide-On BMA Jack To:				
SMA Female		PE91400	B4	26
SMA Female	(PM)	PE91399	C4	26
Slide-On BMA Plug To:				
SMA Female		PE91398	E3	26
SMA Female	(B)	PE91402	A4	26
SMA Male		PE91396	C3	26
SMA Male	(B)	PE91401	D3	26
SMA Female To:				
1.0/2.3 Jack		PE9693	E2	38
1.0/2.3 Plug		PE9691	D2	38
1.85mm Female		PE9729	B3	38
1.85mm Male		PE9726	A3	38
2.4mm Female	(P)	PE9656	D3	38
2.4mm Male		PE9655	C3	38
2.4mm NMD Female	(RU)	PE91146	D4	20
2.92mm Female	(P)	PE91011	A4	38
2.92mm Male	(P)	PE91009	E3	38
3.5mm Female		PE9725	C4	38
3.5mm Male		PE9724	B4	38
3.5mm NMD Female	(RU)	PE91147	A2	23
4.3-10 Male	(LP)	PE91484	E2	24
7/16 DIN Female	(LP)	PE91042	C5	38
7/16 DIN Male	(LP)	PE91036	A5	38
7/16 DIN Male		PE91175	B5	38
75 Ohm F Female		PE91002	A7	38
75 Ohm F Male		PE91045	E6	38
7mm Sexless	(P)	PE9214	D4	38
7mm Sexless	(P) (PM)	PE9327	E4	38
BNC Female		PE9075	A6	38
BNC Female		PE9496	B6	38
BNC Female	(B)	PE9185	C6	38
BNC Female	(B)	PE9407	D6	38
BNC Male		PE9073	D5	38
BNC Male		PE9494	E5	38
FME Jack		PE9708	C7	38
FME Plug		PE9703	B7	38
Full Detent Mini SMP Male		PE91299	D1	39
Full Detent Mini SMP Male		PE91129	A2	39
Full Detent SMP Male		PE91305	A7	39
Full Detent SMP Male	(P)	PE91056	E7	39
Full Detent SMP Male	(B) (PM)	PE91054	C1	40
Full Detent SMP Male	(P) (PM)	PE91058	E1	40
GR874 Sexless		PE9260	D7	38
HN Female		PE9255	A1	39
HN Male		PE9253	E7	38
Limited Detent SMP Male		PE91306	B7	39
Limited Detent SMP Male	(P)	PE91050	D7	39
Limited Detent SMP Male	(P)	PE9512	A1	40
Limited Detent SMP Male		PE9778	B1	40
Limited Detent SMP Male	(P) (PM)	PE91066	B2	40
MCX Jack		PE9470	C1	39
MCX Plug		PE9471	B1	39
Mini SMP Female		PE91301	B2	39
Mini SMP Female	(P)	PE91051	C2	39
MMCX Jack		PE9477	B3	39
MMCX Plug		PE9475	A3	39
N Female		PE9083	C4	39
N Female	(P)	PE9432	D4	39
N Female	(B)	PE9252	E4	39
N Female	(B) (P)	PE9486	A5	39
N Female	(PM)	PE9104	B5	39
N Female	(P) (PM)	PE9434	C5	39
N Female	(B)	PE9408	D5	39
N Female	(B) (P) (PM)	PE9435	E5	39
N Male		PE9081	C3	39
N Male	(B)	PE9551	E3	39
N Male	(PM)	PE9275	A4	39
N Male	(P) (PM)	PE9498	B4	39
N Male	(LP)	PE91177	C4	32
N Male	(P)	PE91339	D4	32
Push-On SMA Male	(PO)	PE91336	A5	37
QD N Male	(QD)	PE9684	D3	39
QMA Male		PE9786	A6	39
Rev. Pol. TNC Female		PE9603	E3	41
Rev. Pol. TNC Male		PE9602	D3	41
Slide-On BMA Jack		PE91400	B4	26
Slide-On BMA Jack	(PM)	PE91399	C4	26
Slide-On BMA Plug		PE91398	E3	26
Slide-On BMA Plug	(B)	PE91402	A4	26
SMB Jack		PE9143	C6	39
SMB Plug		PE9142	B6	39
SMC Jack		PE9147	E6	39
SMC Plug		PE9146	D6	39
Smooth Bore Mini SMP Male		PE91300	E1	39
Smooth Bore SMP Male		PE91307	C7	39
Smooth Bore SMP Male	(P) (PM)	PE91061	A2	40
SMP Female		PE91308	D2	40
SMP Female	(P)	PE91064	E2	40
SMP Female	(P)	PE9779	A3	40
SMP Male	(P) (PM)	PE91057	D1	40
SMP Male	(P) (PM)	PE91059	C2	40
Snap-On MMBX Jack	(SO)	PE91363	E2	39
Snap-On MMBX Plug	(SO)	PE91361	D2	39
Snap-On QMA Male	(SO)	PE91345	D4	34
SSMA Female		PE9399	C3	40
SSMA Male		PE9188	B3	40
SSMB Plug		PE9402	D3	40
SSMC Jack		PE91433	A4	40
SSMC Plug		PE91380	E3	40
TNC Female		PE9079	D4	40
TNC Female		PE9442	E4	40
TNC Female	(B) (PM)	PE9251	A5	40
TNC Female	(PM)	PE9276	B5	40
TNC Male		PE9077	B4	40
TNC Male		PE9440	C4	40
UHF Male		PE9415	C5	40
UMCX Jack		PE91006	E5	40
UMCX Plug		PE91005	D5	40
SMA In-Series:				
Female to Female		PE9070	E6	35
Female to Female		PE9380	A7	35
Female to Female	(P)	PE9695	B7	35
Female to Female	(R)	PE91494	C7	35
Female to Female	(R)	PE91495	D7	35
Female to Female	90º	PE9485	E7	35
Female to Female		PE9246	A1	36
Female to Female	(B) (PM)	PE9014	B1	36
Female to Female	(B)	PE91258	C1	36
Female to Female	(B) (PM)	PE9508	D1	36
Female to Female	(B) (P) (PM)	PE9620	E1	36
Female to Female	(H) (B)	PE91393	A2	36
Female to Female	(B)	PE9184	B2	36
Female to Female	(B)	PE9067	C2	36
Female to Female	(PM)	PE9312	D2	36
Female to Female	(PM)	PE9670	E2	36
Female to Female	(B)	PE9184NH	A3	36
Female to Female	(PM)	PE91290	B3	36
Female to Female	(P)	PE91549	C3	36
Female to Female	90º	PE91176	D3	36
Female to Female		PE91260	B7	40
Female to Male		PE9182	D6	35
Female to Male		PE9533	A7	40
Female to Male		PE9683	C6	41
Male to Female		PE9103	C3	35
Male to Female	(P)	PE9506	D3	35
Male to Female	(QD)	PE9546	E3	35
Male to Female	(P)	PE9694	A4	35
Male to Female	(P) (QD)	PE9774	B4	35
Male to Female	(R)	PE91492	C4	35
Male to Female	(R)	PE91493	D4	35
Male to Female	(R)	PE91155	E4	35
Male to Female	(R)	PE91222	A5	35
Male to Female	90º	PE9068	B5	35
Male to Female	(P) 45º	PE91332	C5	35
Male to Female		PE9247	D5	35
Male to Female	(B)	PE9621	E5	35
Male to Female	(PM)	PE91453	A6	35
Male to Female	(B) (PO)	PE91321	B6	35
Male to Female	(P) 90º	PE91504	C6	35
Male to Female	(QD)	PE91265	C6	40
Male to Female		PE9534	D6	40
Male to Female	90º	PE91264	E6	40
Male to Female		PE9682	B6	41
Male to Male		PE91135	C1	35
Male to Male	(P)	PE9505	D1	35
Male to Male	(R)	PE91496	E1	35
Male to Male	(R)	PE91497	A2	35
Male to Male	90º	PE9418	B2	35
Male to Male		PE9379	C2	35
Male to Male	(P) 90º	PE91151	D2	35
Male to Male	(R) 90º	PE9642	E2	35
Male to Male	(PM)	PE9669	A3	35
Male to Male		PE91535	B3	35
Male to Male		PE91259	B6	40
SMA Male To:				
1.0/2.3 Jack		PE9690	B4	36
1.0/2.3 Plug		PE9692	A4	36
1.85mm Female		PE9728	D4	36
1.85mm Male		PE9727	C4	36
2.4mm Female	(P)	PE9654	A5	36
2.4mm Male	(P)	PE9653	E4	36
2.92mm Female	(P)	PE91008	C5	36
2.92mm Male	(P)	PE91010	B5	36
3.5mm Female		PE91536	E5	36
3.5mm Male		PE9722	D5	36
75 Ohm F Female		PE91003	A7	36
7mm Sexless	(P)	PE9215	A6	36
BNC Female		PE9074	D6	36
BNC Female		PE9495	E6	36
BNC Male		PE9072	B6	36
BNC Male		PE9493	C6	36
FME Jack		PE9707	B7	36
Full Detent Mini SMP Male		PE91302	C1	37
Full Detent Mini SMP Male	(P)	PE91052	E1	37
Full Detent SMP Male		PE91309	A6	37
Full Detent SMP Male	(P)	PE91063	D6	37
GR874 Sexless		PE9259	C7	36
HN Female		PE9256	E7	36
HN Male		PE91448	D7	36
Limited Detent SMP Male		PE91310	B6	37
Limited Detent SMP Male	(P)	PE9511	E6	37
MCX Jack		PE9472	B1	37
MCX Plug		PE9473	A1	37
Mini SMP Female		PE91304	A2	37
Mini SMP Female	(P)	PE91103	B2	37
MMCX Jack		PE9478	A3	37
MMCX Plug		PE9476	E2	37
N Female		PE9082	E3	37
N Female	(P)	PE9433	A4	37
N Female	(B) (P)	PE9487	B4	37
N Female	(PM)	PE9105	C4	37
N Female	(P) (PM)	PE9497	D4	37

Feature: (B) Bulkhead Mount / (H) Hermetically Sealed / (I) Isolated Sealed / (LP) Low PIM / (P) Precision / (PM) Panel Mount / (PO) Push On / (QD) Quick Disconnect / (R) Radius Right Angle / (RU) Ruggedized / (SO) Snap-On

Adapter Locator

Connector Type	Feature	Model No.	C/R	Page
N Female	(B) (P)	PE9488	E4	37
N Female	(LP)	PE91178	D5	33
N Male		PE9080	B3	37
N Male	(P)	PE9431	C3	37
N Male	(P) (PM)	PE9499	D3	37
Rev. Pol. MCX Plug		PE9581	B3	41
Rev. Pol. TNC Female		PE9600	C3	41
Slide-On BMA Plug		PE91396	C3	26
Slide-On BMA Plug	(B)	PE91401	D3	26
SMB Jack		PE9145	C5	37
SMB Plug		PE9144	B5	37
SMC Jack		PE9149	E5	37
SMC Plug		PE9148	D5	37
Smooth Bore Mini SMP Male		PE91303	D1	37
Smooth Bore SMP Male		PE91311	C6	37
SMP Female		PE91312	A7	37
SMP Female	(P)	PE91062	B7	37
SMP Female	(P)	PE9513	C7	37
Snap-On MMBX Jack	(SO)	PE91362	D2	37
Snap-On MMBX Plug	(SO)	PE91360	C2	37
Snap-On QMA Female	(SO)	PE91346	E4	34
SSMA Female		PE9063	E7	37
SSMA Male		PE9187	D7	37
SSMB Jack		PE9401	A1	38
TNC Female		PE91507	E1	38
TNC Female		PE9078	D1	38
TNC Female	(PM)	PE9384	A2	38
TNC Male		PE9076	B1	38
TNC Male		PE9439	C1	38
UHF Female		PE9400	B2	38
UMCX Jack		PE91007	C2	38
SMB In-Series:				
Jack to Jack		PE9116	E7	41
Jack to Jack		PE9302	A1	42
Jack to Jack	(B) (PM)	PE9122	B1	42
Jack to Plug		PE9243	D7	41
Plug to Jack		PE9120	B7	41
Plug to Jack		PE9309	C7	41
Plug to Plug		PE9118	E6	41
Plug to Plug		PE9310	A7	41
SMB Jack To:				
BNC Female		PE9136	C2	42
BNC Female	(B)	PE9240	D2	42
BNC Male		PE9132	B2	42
N Female		PE9315	A6	33
N Male		PE9313	A5	32
SMA Female		PE9143	C6	39
SMA Male		PE9145	C5	37
SMC Jack		PE9283	B6	42
SMC Plug		PE9284	B5	42
SMB Plug To:				
BNC Female		PE9137	E1	42
BNC Female	(B) (PM)	PE9241	A2	42
BNC Male		PE9135	D1	42
N Female		PE9316	E5	33
N Male		PE9314	E4	32
SMA Female		PE9142	B6	39
SMA Male		PE9144	B5	37
SMC Jack		PE9282	A6	42
SMC Plug		PE9281	A5	42
SMC In-Series:				
Jack to Jack		PE9304	A4	42
Jack to Jack	(B) (PM)	PE91403	B4	42
Jack to Plug		PE9242	E3	42
Plug to Jack		PE9119	C3	42
Plug to Jack	90º	PE9303	D3	42
Plug to Plug		PE9117	A3	42
Plug to Plug		PE9305	B3	42
SMC Jack To:				
BNC Female		PE9140	D5	42
BNC Female	(B)	PE9108	E5	42
BNC Male		PE9138	C5	42
N Female		PE9319	C6	33
N Male		PE9317	C5	32
SMA Female		PE9147	E6	39
SMA Male		PE9149	E5	37
SMB Jack		PE9283	B6	42
SMB Plug		PE9282	A6	42
TNC Male		PE9226	C7	44
SMC Plug To:				
BNC Female		PE9141	E4	42
BNC Male		PE9139	D4	42
N Female		PE9320	B6	33
N Male		PE9318	B5	32
SMA Female		PE9146	D6	39
SMA Male		PE9148	D5	37
SMB Jack		PE9284	B5	42
SMB Plug		PE9281	A5	42
Smooth Bore Mini SMP Male To:				
2.92mm Female		PE91128	D6	21
2.92mm Male		PE91125	C3	21
SMA Female		PE91300	E1	39
SMA Male		PE91303	D1	37
Smooth Bore SMP Male To:				
SMA Female		PE91307	C7	39
SMA Female	(P) (PM)	PE91061	A2	40
SMA Male		PE91311	C6	37
SMP Female To:				
2.4mm Female		PE91055	D2	20
2.92mm Female		PE91060	C7	21
SMA Female		PE91308	D2	40
SMA Female	(P)	PE91064	E2	40
SMA Female	(P)	PE9779	A3	40
SMA Male		PE91312	A7	37
SMA Male	(P)	PE91062	B7	37
SMA Male	(P)	PE9513	C7	37
SMP Female		PE91065	D1	43
SMP Female		PE91065	D1	43
SMP In-Series:				
Female to Female		PE91102	D6	42
Female to Female		PE9776	E6	42
Female to Female		PE91068	A7	42
Female to Female		PE91072	B7	42
Female to Female		PE91099	C7	42
Female to Female		PE91101	D7	42
Female to Female		PE9775	E7	42
Female to Female		PE9777	A1	43
SMP Male To:				
2.4mm Female		PE91048	C2	20
SMA Female	(P) (PM)	PE91057	D1	40
SMA Female	(P) (PM)	PE91059	C2	40
Snap-On MMBX Jack To:				
SMA Female	(SO)	PE91363	E2	39
SMA Male	(SO)	PE91362	D2	37
Snap-On MMBX Plug To:				
Push-On SMP Female	(PO) (SO)	PE91364	C1	43
SMA Female	(SO)	PE91361	D2	39
SMA Male	(SO)	PE91360	C2	37
Snap-On QMA Female To:				
SMA Male	(SO)	PE91346	E4	34
Snap-On SMA Female	(SO)	PE91347	A5	34
Snap-On QMA Male To:				
SMA Female	(SO)	PE91345	D4	34
Snap-On SMA Male	(SO)	PE91344	C4	34
Snap-On SMA Female To:				
Snap-On QMA Female	(SO)	PE91347	A5	34
Snap-On SMA Male To:				
Snap-On QMA Male	(SO)	PE91344	C4	34
SSMA Female To:				
BNC Male		PE9191	A4	43
N Female		PE9354	C4	43
N Male		PE9352	B4	43
SMA Female		PE9399	C3	40
SMA Male		PE9063	E7	37
SSMA In-Series:				
Female to Female		PE9192	E2	43
Female to Female	(B) (PM)	PE9189	A3	43
Male to Female		PE9358	B2	43
Male to Female	(QD)	PE9685	C2	43
Male to Female	90º	PE9334	D2	43
Male to Male		PE9357	A2	43
SSMA Male To:				
2.92mm Female		PE9768	D7	21
BNC Female		PE91046	D3	43
BNC Male		PE9213	C3	43
N Male		PE9351	E3	43
SMA Female		PE9188	B3	40
SMA Male		PE9187	D7	37
SSMB Jack To:				
BNC Female		PE9394	B5	43
SMA Male		PE9401	A1	38
SSMB Plug To:				
BNC Female		PE9395	A5	43
BNC Male		PE9393	E4	43
SMA Female		PE9402	D3	40
SSMC In-Series:				
Jack to Jack	(B)	PE91432	A6	43
Plug to Jack		PE91434	E5	43
Plug to Plug		PE91436	D5	43
SSMC Jack To:				
SMA Female		PE91433	A4	40
SSMC Plug To:				
SMA Female		PE91380	E3	40
TNC Female To:				
7/16 DIN Female		PE91392	A1	45
7mm Sexless	(P)	PE9218	E7	44
BNC Female		PE9097	C1	45
BNC Male		PE9098	B1	45
C Male		PE9564	D1	45
FME Jack		PE9714	E1	45
Limited Detent SMP Male	(B)	PE91073	E2	45
MCX Jack		PE9544	B2	45
MCX Jack	(B) (PM)	PE9521	C2	45
MCX Plug		PE9545	A2	45
Mini UHF Male		PE9346	D2	45
N Female		PE9131	B7	33
N Female	(P)	PE9449	C7	33
N Female	(PM)	PE9552	D7	33
N Female	(B)	PE9482	E7	33
N Female	(P) (PM)	PE9450	A1	34
N Male		PE9090	A6	32
N Male	90º	PE9550	B6	32
N Male		PE91537	C6	32
Rev. Pol. SMA Female		PE9599	A5	41
Rev. Pol. SMA Male		PE9596	C4	41
SMA Female		PE9079	D4	40
SMA Female		PE9442	E4	40
SMA Female	(B) (PM)	PE9251	A5	40
SMA Female	(PM)	PE9276	B5	40
SMA Male		PE91507	E1	38
SMA Male		PE9078	D1	38
SMA Male	(PM)	PE9384	A2	38
TNC Female	(LP)	PE1279	A3	45
TNC Female	(LP)	PE1279	A3	45
UHF Male		PE9372	B3	45
TNC In-Series:				
Female to Female		PE91204	D2	44
Female to Female		PE91241	E2	44
Female to Female		PE9099	A3	44
Female to Female	(LP)	PE91174	B3	44
Female to Female		PE91381	C3	44
Female to Female	(B)	PE91430	D3	44
Female to Female	(B)	PE9154	E3	44
Female to Female	(PM)	PE9288	A4	44
Female to Female	(B)	PE91205	B4	44
Female to Female	(B)	PE91242	C4	44
Female to Female	(B)	PE9287	D4	44
Female to Male		PE9195	C2	44
Female to Male		PE9531	E3	45
Male to Female		PE91203	D7	43
Male to Female		PE91240	E7	43
Male to Female	(P)	PE91505	A1	44
Male to Female	(LP)	PE91173	B1	44
Male to Female		PE9270	C1	44
Male to Female	(P)	PE9443	D1	44
Male to Female	(QD)	PE9561	E1	44
Male to Female	90º	PE9100	A2	44
Male to Female		PE9290	B2	44
Male to Female		PE9532	D3	45
Male to Male	(LP)	PE91172	C6	43
Male to Male		PE91202	D6	43
Male to Male		PE91239	E6	43
Male to Male		PE9091	A7	43
Male to Male		PE9445	B7	43
Male to Male	90º	PE9560	C7	43
TNC Male To:				
7/16 DIN Female		PE9638	B5	44
7mm Sexless	(P)	PE9219	A5	44
BNC Female		PE9088	C5	44
BNC Female	90º	PE9783	D5	44
C Female		PE9562	E5	44
FME Jack		PE9713	C6	44
FME Plug		PE9699	A6	44
FME Plug	90º	PE9700	B6	44
HN Male		PE9563	D6	44
MCX Jack		PE9542	A7	44
MCX Plug		PE9543	E6	44
Mini UHF Female		PE9345	B7	44
N Female		PE9089	D6	33
N Female	(P)	PE91506	E6	33
N Female	90º	PE9263	A7	33
N Male		PE9130	D5	32
N Male	(P)	PE9446	E5	32
Rev. Pol. SMA Female		PE9598	E4	41
Rev. Pol. SMA Male		PE9597	B4	41
SMA Female		PE9077	B4	40
SMA Female		PE9440	C4	40
SMA Male		PE9076	B1	38
SMA Male		PE9439	C1	38
SMC Jack		PE9226	C7	44
UHF Female		PE9291	D7	44
UHF Female To:				
75 Ohm F Female		PE9167	B7	45
BNC Female		PE9421	A7	45
BNC Male		PE91329	E6	45
Mini UHF Male		PE91447	C7	45
N Female		PE9385	C1	34
N Male		PE9111	E6	32
SMA Male		PE9400	B2	38
TNC Male		PE9291	D7	44
UHF In-Series:				
Female to Female	(B) (PM)	PE9114	C5	45
Female to Male		PE9095	B5	45
Male to Female	90º	PE9209	A5	45
Male to Male		PE91487	E4	45
UHF Male To:				
75 Ohm F Female		PE9165	B6	45
BNC Female		PE91328	A6	45
BNC Male		PE9201	E5	45
FME Plug		PE9701	C6	45
Mini UHF Female		PE9348	D6	45
N Female		PE9112	B1	34
N Male		PE9113	D6	32
SMA Female		PE9415	C5	40
TNC Female		PE9372	B3	45
UMCX Jack To:				
SMA Female		PE91006	E5	40
SMA Male		PE91007	C2	38
UMCX Plug To:				
SMA Female		PE91005	D5	40

Feature: (B) Bulkhead Mount / (H) Hermetically Sealed / (I) Isolated Sealed / (LP) Low PIM / (P) Precision / (PM) Panel Mount / (PO) Push On / (QD) Quick Disconnect / (R) Radius Right Angle / (RU) Ruggedized / (SO) Snap-On

LOW PIM ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	**2.2-5 In-Series** →	 PRICE 1-24 $56.99; 25-49 $54.14; 50-99 $51.29; 100+ $49.01 (Low PIM) **2.2-5 Male to 2.2-5 Male** VSWR 1.25:1 to 8 GHz **Model No:** PE9792	 PRICE 1-24 $56.99; 25-49 $54.14; 50-99 $51.29; 100+ $49.01 (Low PIM) **2.2-5 Female to 2.2-5 Female** VSWR 1.25:1 to 8 GHz **Model No:** PE9793	**4.1/9.5 Mini DIN Between Series** →	 PRICE 1-24 $75.99; 25-49 $72.19; 50-99 $68.39; 100+ $65.35 (Low PIM) **4.1/9.5 Mini DIN Male to N Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91092
2	 PRICE 1-24 $73.99; 25-49 $70.29; 50-99 $66.59; 100+ $63.63 (Low PIM) **4.1/9.5 Mini DIN Male to N Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91093	 PRICE 1-24 $75.99; 25-49 $72.19; 50-99 $68.39; 100+ $65.35 (Low PIM) **4.1/9.5 Mini DIN Female to N Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91094	 PRICE 1-24 $75.99; 25-49 $72.19; 50-99 $68.39; 100+ $65.35 (Low PIM) **4.1/9.5 Mini DIN Female to N Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91095	**4.3 Non Constant In-Series** →	 PRICE 1-24 $45.19; 25-49 $42.93; 50-99 $40.67; 100+ $38.86 (Low PIM) **4.3-10 Male to 4.3-10 Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91466
3	 PRICE 1-24 $101.99; 25-49 $96.89; 50-99 $91.79; 100+ $87.71 (Low PIM) **4.3-10 Male to 4.3-10 Male** VSWR 1.08:1 to 6 GHz **Model No:** PE91385	 PRICE 1-24 $50.99; 25-49 $48.44; 50-99 $45.89; 100+ $43.85 (Low PIM) **4.3-10 Male to 4.3-10 Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91465	 PRICE 1-24 $101.99; 25-49 $96.89; 50-99 $91.79; 100+ $87.71 (Low PIM) **4.3-10 Male to 4.3-10 Female Right Angle** VSWR 1.2:1 to 3 GHz **Model No:** PE91467	 PRICE 1-24 $103.99; 25-49 $99.83; 50-99 $96.71; 100+ $94.63 (Low PIM) **4.3-10 Male to 4.3-10 Female** VSWR 1.08:1 to 6 GHz **Model No:** PE91387	 PRICE 1-24 $50.99; 25-49 $48.44; 50-99 $45.89; 100+ $43.85 (Low PIM) **4.3-10 Female to 4.3-10 Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91464
4	 PRICE 1-24 $105.99; 25-49 $100.69; 50-99 $95.39; 100+ $91.15 (Low PIM) **4.3-10 Female to 4.3-10 Female** VSWR 1.08:1 to 6 GHz **Model No:** PE91386	**4.3 Non Constant Between Series** →	 PRICE 1-24 $45.19; 25-49 $42.93; 50-99 $40.67; 100+ $38.86 (Low PIM) **4.3-10 Male to N Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91476	 PRICE 1-24 $61.99; 25-49 $58.89; 50-99 $55.79; 100+ $53.31 (Low PIM) **QD 4.3-10 Male to N Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91480	 PRICE 1-24 $45.19; 25-49 $42.93; 50-99 $40.67; 100+ $38.86 (Low PIM) **4.3-10 Male to N Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91474
5	 PRICE 1-24 $45.19; 25-49 $42.93; 50-99 $40.67; 100+ $38.86 (Low PIM) **4.3-10 Male to N Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91477	 PRICE 1-24 $59.99; 25-49 $56.99; 50-99 $53.99; 100+ $51.59 (Low PIM) **QD 4.3-10 Male to N Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91478	 PRICE 1-24 $71.99; 25-49 $68.39; 50-99 $64.79; 100+ $61.91 (Low PIM) **4.3-10 Male to N Female Right Angle** VSWR 1.25:1 to 6 GHz **Model No:** PE91483	 PRICE 1-24 $107.99; 25-49 $102.59; 50-99 $97.19; 100+ $92.87 (Low PIM) **4.3-10 Male to N Female** VSWR 1.08:1 to 6 GHz **Model No:** PE91389	 PRICE 1-24 $40.79; 25-49 $38.75; 50-99 $36.71; 100+ $35.08 (Low PIM) **4.3-10 Male to SMA Female** VSWR 1.15:1 to 6 GHz **Model No:** PE91484
6	 PRICE 1-24 $52.99; 25-49 $50.34; 50-99 $47.69; 100+ $45.57 (Low PIM) **4.3-10 Female to N Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91479	 PRICE 1-24 $49.99; 25-49 $47.49; 50-99 $44.99; 100+ $42.99 (Low PIM) **QD 4.3-10 Female to N Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91481	 PRICE 1-24 $46.19; 25-49 $43.88; 50-99 $41.57; 100+ $39.72 (Low PIM) **4.3-10 Female to N Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91475	 PRICE 1-24 $49.79; 25-49 $47.30; 50-99 $44.81; 100+ $42.82 (Low PIM) **QD 4.3-10 Female to N Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91482	**7/16 DIN In-Series** →
7	 PRICE 1-9 $165.99; 10-24 $157.69; 25-49 $149.39; 50+ $142.75 (Low PIM) **7/16 DIN Male to 7/16 DIN Male** Max. Freq. 8 GHz **Model No:** PE91039	 PRICE 1-9 $135.99; 10-24 $129.19; 25-49 $122.39; 50+ $116.95 (Low PIM) **7/16 DIN Male to 7/16 DIN Female** Max. Freq. 8 GHz **Model No:** PE91028	 PRICE 1-9 $135.99; 10-24 $129.19; 25-49 $122.39; 50+ $116.95 (Low PIM) **7/16 DIN Female to 7/16 DIN Female** Max. Freq. 8 GHz **Model No:** PE91029	 PRICE 1-9 $179.99; 10-24 $170.99; 25-49 $161.99; 50+ $154.79 (Low PIM) **7/16 DIN Female to 7/16 DIN Female Bulkhead** Max. Freq. 8 GHz **Model No:** PE91038	**7/16 DIN Between Series** →

See Our Website For Current Pricing & Real-Time Stock Availability!

LOW PIM ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 Low PIM PRICE 1-24 $56.99 25-49 $54.14 50-99 $51.29 100+ $49.01 **7/16 DIN Male to 2.2-5 Male** VSWR 1.25:1 to 8 GHz **Model No:** PE9798	 Low PIM PRICE 1-24 $56.99 25-49 $54.14 50-99 $51.29 100+ $49.01 **7/16 DIN Male to 2.2-5 Female** VSWR 1.25:1 to 8 GHz **Model No:** PE9799	 Low PIM PRICE 1-24 $98.99 25-49 $94.04 50-99 $89.09 100+ $85.13 **7/16 DIN Male to 4.1/9.5 Mini DIN Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91088	 Low PIM PRICE 1-24 $47.19 25-49 $44.83 50-99 $42.47 100+ $40.58 **7/16 DIN Male to 4.3-10 Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91468	 Low PIM PRICE 1-24 $50.99 25-49 $48.44 50-99 $45.89 100+ $43.85 **7/16 DIN Male to 4.3-10 Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91469
2	 Low PIM PRICE 1-24 $87.99 25-49 $83.59 50-99 $79.19 100+ $75.67 **7/16 DIN Male to 4.3-10 Female** VSWR 1.08:1 to 6 GHz **Model No:** PE91390	 Low PIM PRICE 1-24 $98.99 25-49 $94.04 50-99 $89.09 100+ $85.13 **7/16 DIN Female to 4.1/9.5 Mini DIN Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91090	 Low PIM PRICE 1-24 $98.99 25-49 $94.04 50-99 $89.09 100+ $85.13 **7/16 DIN Female to 4.1/9.5 Mini DIN Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91091	 Low PIM PRICE 1-24 $49.99 25-49 $47.49 50-99 $44.99 100+ $42.99 **7/16 DIN Female to 4.3-10 Male** VSWR 1.2:1 to 6 GHz **Model No:** PE91470	 Low PIM PRICE 1-24 $68.99 25-49 $65.54 50-99 $62.09 100+ $59.33 **7/16 DIN Female to QD 4.3-10 Male** VSWR 1.2:1 to 6 GHz **Model No:** PE91472
3	 Low PIM PRICE 1-9 $141.99 10-24 $134.89 25-49 $127.79 50+ $122.11 **7/16 DIN Female to 4.3-10 Male** VSWR 1.08:1 to 6 GHz **Model No:** PE91391	 Low PIM PRICE 1-24 $50.99 25-49 $48.44 50-99 $45.89 100+ $43.85 **7/16 DIN Female to 4.3-10 Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91471	 Low PIM PRICE 1-24 $51.99 25-49 $49.39 50-99 $46.79 100+ $44.71 **7/16 DIN Female to QD 4.3-10 Female** VSWR 1.2:1 to 6 GHz **Model No:** PE91473	 Low PIM PRICE 1-9 $107.99 10-24 $102.59 25-49 $99.35 50+ $96.11 **7/16 DIN Female to 7/16 DIN Female Bulkhead** Max. Freq. 6 GHz **Model No:** PE1280	***N In-Series***
4	 Low PIM PRICE 1-24 $123.99 25-49 $117.79 50-99 $111.59 100+ $106.63 **N Male to N Male** Max. Freq. 12.4 GHz **Model No:** PE91034	 Low PIM PRICE 1-24 $123.99 25-49 $117.79 50-99 $111.59 100+ $106.63 **N Male to N Female** Max. Freq. 12.4 GHz **Model No:** PE91040	 Low PIM PRICE 1-24 $90.99 25-49 $86.44 50-99 $81.89 100+ $78.25 **N Female to N Female** VSWR 1.2:1 to 6 GHz **Model No:** PE91140	 Low PIM PRICE 1-24 $81.99 25-49 $77.89 50-99 $73.79 100+ $70.51 **N Female to N Female Bulkhead** VSWR 1.2:1 to 6 GHz **Model No:** PE91179	***N Between Series***
5	 Low PIM PRICE 1-24 $93.99 25-49 $89.29 50-99 $84.59 100+ $80.83 **N Male to 4.3-10 Female** VSWR 1.08:1 to 6 GHz **Model No:** PE91388	 Low PIM PRICE 1-24 $133.99 25-49 $127.29 50-99 $120.59 100+ $115.23 **N Male to 7/16 DIN Female** Max. Freq. 8 GHz **Model No:** PE91032	 Low PIM PRICE 1-24 $60.99 25-49 $57.94 50-99 $54.89 100+ $52.45 **N Male to SMA Female** VSWR 1.2:1 to 6 GHz **Model No:** PE91177	 Low PIM PRICE 1-24 $56.99 25-49 $54.14 50-99 $51.29 100+ $49.01 **N Male to 2.2-5 Male** VSWR 1.25:1 to 8 GHz **Model No:** PE9796	 Low PIM PRICE 1-24 $53.99 25-49 $51.29 50-99 $48.59 100+ $46.43 **N Male to 2.2-5 Female** VSWR 1.25:1 to 8 GHz **Model No:** PE9797
6	 Low PIM PRICE 1-24 $125.99 25-49 $119.69 50-99 $113.39 100+ $108.35 **N Female to 7/16 DIN Male** Max. Freq. 8 GHz **Model No:** PE91031	 Low PIM PRICE 1-9 $177.99 10-24 $169.09 25-49 $160.19 50+ $153.07 **N Female to 7/16 DIN Female** Max. Freq. 8 GHz **Model No:** PE9180	 Low PIM PRICE 1-24 $61.99 25-49 $58.89 50-99 $55.79 100+ $53.31 **N Female to SMA Male** VSWR 1.2:1 to 6 GHz **Model No:** PE91178	 Low PIM PRICE 1-24 $56.99 25-49 $54.14 50-99 $51.29 100+ $49.01 **N Female to 2.2-5 Male** VSWR 1.25:1 to 8 GHz **Model No:** PE9794	 Low PIM PRICE 1-24 $53.99 25-49 $51.29 50-99 $48.59 100+ $46.43 **N Female to 2.2-5 Female** VSWR 1.25:1 to 8 GHz **Model No:** PE9795
7	***SMA Between Series***	 Low PIM PRICE 1-24 $107.99 25-49 $102.59 50-99 $97.19 100+ $92.87 **SMA Female to 7/16 DIN Male** VSWR 1.09:1 to 7.5 GHz **Model No:** PE91036	 Low PIM PRICE 1-24 $107.99 25-49 $102.59 50-99 $97.19 100+ $92.87 **SMA Female to 7/16 DIN Female** Max. Freq. 8 GHz **Model No:** PE91042	***TNC In-Series***	 Low PIM PRICE 1-24 $78.99 25-49 $75.04 50-99 $71.09 100+ $67.93 **TNC Male to TNC Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91172

See Our Website For Current Pricing & Real-Time Stock Availability!

LOW PIM ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 Low PIM PRICE 1-24 $74.99 25-49 $71.24 50-99 $67.49 100+ $64.49 **TNC Male to TNC Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91173	 Low PIM PRICE 1-24 $68.99 25-49 $65.54 50-99 $62.09 100+ $59.33 **TNC Female to TNC Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91174	***TNC Between Series*** →	 Low PIM PRICE 1-9 $57.99 10-24 $55.09 25-49 $53.35 50+ $51.61 **TNC Female to TNC Female** Max. Freq. 6 GHz **Model No:** PE1279	***Visit pasternack.com for our complete offering of adapters***

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

4	***1.0mm In-Series*** →	 PRICE 1-24 $1,990.00 25-49 $1,850.70 50-99 $1,711.40 100+ $1,592.00 **1.0mm Male to 1.0mm Male** VSWR 1.28:1 to 110 GHz **Model No:** PE91462	 PRICE 1-1 $2,070.00 2-4 $1,987.20 5-9 $1,904.40 10+ $1,821.60 **1.0mm Female to 1.0mm Male** VSWR 1.28:1 to 110 GHz **Model No:** PE91461	 PRICE 1-1 $2,040.00 2-4 $1,958.40 5-9 $1,876.80 10+ $1,795.20 **1.0mm Female to 1.0mm Female** VSWR 1.28:1 to 110 GHz **Model No:** PE91463	***1.0mm Between Series*** →
5	 PRICE 1-4 $855.00 5-9 $812.25 10-24 $769.50 25+ $735.30 **1.0mm Male to 1.85mm Male** VSWR 1.25:1 to 65 GHz **Model No:** PE91118	 PRICE 1-4 $720.00 5-9 $684.00 10-24 $648.00 25+ $619.20 **1.0mm Male to 1.85mm Female** VSWR 1.35:1 to 65 GHz **Model No:** PE91108	 PRICE 1-4 $695.00 5-9 $660.25 10-24 $625.50 25+ $597.70 **1.0mm Female to 1.85mm Male** VSWR 1.25:1 to 65 GHz **Model No:** PE91119	 PRICE 1-4 $720.00 5-9 $684.00 10-24 $648.00 25+ $619.20 **1.0mm Female to 1.85mm Female** VSWR 1.35:1 to 65 GHz **Model No:** PE91109	***1.85mm In-Series*** →
6	 PRICE 1-4 $910.00 5-9 $864.50 10-24 $819.00 25+ $782.60 **1.85mm Male to 1.85mm Male** VSWR 1.35:1 to 67 GHz **Model No:** PE91085	 PRICE 1-4 $830.00 5-9 $788.50 10-24 $747.00 25+ $713.80 **1.85mm Male to 1.85mm Male** VSWR 1.5:1 to 65 GHz **Model No:** PE9716	 PRICE 1-24 $880.00 25-49 $836.00 50-99 $792.00 100+ $756.80 **1.85mm Male to 1.85mm Male Right Angle** VSWR 1.35:1 to 67 GHz **Model No:** PE1277	 PRICE 1-4 $835.00 5-9 $793.25 10-24 $751.50 25+ $718.10 **1.85mm Male to 1.85mm Female** VSWR 1.35:1 to 67 GHz **Model No:** PE91086	 PRICE 1-4 $830.00 5-9 $788.50 10-24 $747.00 25+ $713.80 **1.85mm Male to 1.85mm Female** VSWR 1.5:1 to 65 GHz **Model No:** PE9715
7	 PRICE 1-24 $880.00 25-49 $836.00 50-99 $792.00 100+ $756.80 **1.85mm Male to 1.85mm Female Right Angle** VSWR 1.35:1 to 67 GHz **Model No:** PE1276	 PRICE 1-4 $845.00 5-9 $802.75 10-24 $760.50 25+ $726.70 **1.85mm Female to 1.85mm Female** Max. Freq. 67 GHz **Model No:** PE91084	 PRICE 1-4 $700.00 5-9 $665.00 10-24 $630.00 25+ $602.00 **1.85mm Female to 1.85mm Female** VSWR 1.25:1 to 67 GHz **Model No:** PE91115	 PRICE 1-24 $880.00 25-49 $836.00 50-99 $792.00 100+ $756.80 **1.85mm Female to 1.85mm Female Right Angle** VSWR 1.35:1 to 67 GHz **Model No:** PE1278	***1.85mm Between Series*** →

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-9 $489.99 10-24 $465.49 25-49 $440.99 50+ $421.39 **1.85mm Male to 2.4mm Male Right Angle** VSWR 1.4:1 to 50 GHz **Model No:** PE91157	 PRICE 1-9 $447.99 10-24 $425.59 25-49 $403.19 50+ $385.27 **1.85mm Male to 2.4mm Male Miter Right Angle** VSWR 1.35:1 to 50 GHz **Model No:** PE91518	 PRICE 1-9 $499.99 10-24 $474.99 25-49 $449.99 50+ $429.99 **1.85mm Male to 2.4mm Female Miter Right Angle** VSWR 1.35:1 to 50 GHz **Model No:** PE91511	 PRICE 1-24 $463.99 25-49 $431.51 50-99 $399.03 100+ $371.19 **1.85mm Male to 2.92mm Male Right Angle** VSWR 1.3:1 to 40 GHz **Model No:** PE91161	 PRICE 1-9 $411.99 10-24 $391.39 25-49 $370.79 50+ $354.31 **1.85mm Male to 2.92mm Male Miter Right Angle** VSWR 1.25:1 to 40 GHz **Model No:** PE91519
2	 PRICE 1-9 $457.99 10-24 $435.09 25-49 $412.19 50+ $393.87 **1.85mm Male to 2.92mm Female Right Angle** VSWR 1.25:1 to 40 GHz **Model No:** PE91527	 PRICE 1-9 $251.99 10-24 $239.39 25-49 $226.79 50+ $216.71 **1.85mm Male to 3.5mm Female** VSWR 1.3:1 to 34 GHz **Model No:** PE9747	 PRICE 1-9 $269.99 10-24 $256.49 25-49 $242.99 50+ $232.19 **1.85mm Male to N Male** VSWR 1.25:1 to 18 GHz **Model No:** PE9718	 PRICE 1-9 $275.99 10-24 $262.19 25-49 $248.39 50+ $237.35 **1.85mm Male to N Female** VSWR 1.25:1 to 18 GHz **Model No:** PE9719	 PRICE 1-24 $489.99 25-49 $465.49 50-99 $440.99 100+ $421.39 **1.85mm Female to 2.4mm Female Miter Right Angle** VSWR 1.35:1 to 50 GHz **Model No:** PE91534
3	 PRICE 1-24 $463.99 25-49 $431.51 50-99 $399.03 100+ $371.19 **1.85mm Female to 2.92mm Male Right Angle** VSWR 1.3:1 to 40 GHz **Model No:** PE91162	 PRICE 1-24 $419.99 25-49 $390.59 50-99 $361.19 100+ $335.99 **1.85mm Female to 2.92mm Male Miter Right Angle** VSWR 1.25:1 to 40 GHz **Model No:** PE91512	 PRICE 1-24 $335.99 25-49 $312.47 50-99 $288.95 100+ $268.79 **1.85mm Female to 2.92mm Female Right Angle** VSWR 1.3:1 to 40 GHz **Model No:** PE91163	 PRICE 1-24 $405.99 25-49 $377.57 50-99 $349.15 100+ $324.79 **1.85mm Female to 2.92mm Female Miter Right Angle** VSWR 1.25:1 to 40 GHz **Model No:** PE91513	 PRICE 1-9 $291.99 10-24 $277.39 25-49 $262.79 50+ $251.11 **1.85mm Female to N Male** VSWR 1.25:1 to 18 GHz **Model No:** PE9720
4	 PRICE 1-9 $275.99 10-24 $262.19 25-49 $248.39 50+ $237.35 **1.85mm Female to N Female** VSWR 1.25:1 to 18 GHz **Model No:** PE9721	***2.4mm In-Series*** 	 PRICE 1-9 $263.99 10-24 $250.79 25-49 $237.59 50+ $227.03 **2.4mm Male to 2.4mm Male** VSWR 1.3:1 to 50 GHz **Model No:** PE9451	 PRICE 1-9 $253.99 10-24 $241.29 25-49 $228.59 50+ $218.43 **2.4mm Male to 2.4mm Female** VSWR 1.3:1 to 50 GHz **Model No:** PE9452	 PRICE 1-24 $429.99 25-49 $399.89 50-99 $369.79 100+ $343.99 **2.4mm Male to 2.4mm Female Miter Right Angle** VSWR 1.35:1 to 50 GHz **Model No:** PE91498
5	 PRICE 1-9 $249.99 10-24 $237.49 25-49 $224.99 50+ $214.99 **2.4mm Female to 2.4mm Female** VSWR 1.3:1 to 50 GHz **Model No:** PE9453	 PRICE 1-24 $245.99 25-49 $233.69 50-99 $221.39 100+ $211.55 **2.4mm Female to 2.4mm Female Bulkhead** VSWR 1.3:1 to 50 GHz **Model No:** PE91459	 PRICE 1-9 $520.00 10-24 $494.00 25-49 $468.00 50+ $447.20 **2.4mm Female to 2.4mm Female Bulkhead** VSWR 1.35:1 to 50 GHz **Model No:** PE9640	 PRICE 1-24 $407.99 25-49 $379.43 50-99 $350.87 100+ $326.39 **2.4mm Female to 2.4mm Female Miter Right Angle** VSWR 1.35:1 to 50 GHz **Model No:** PE91529	***2.4mm Between Series*** 
6	 PRICE 1-4 $755.00 5-9 $717.25 10-24 $679.50 25+ $649.30 **2.4mm Male to 1.85mm Male** VSWR 1.3:1 to 50 GHz **Model No:** PE9672	 PRICE 1-4 $395.99 5-9 $376.19 10-24 $356.39 25+ $340.55 **2.4mm Male to 1.85mm Male** VSWR 1.3:1 to 50 GHz **Model No:** PE91540	 PRICE 1-9 $449.99 10-24 $427.49 25-49 $404.99 50+ $386.99 **2.4mm Male to 1.85mm Female** VSWR 1.3:1 to 50 GHz **Model No:** PE9674	 PRICE 1-24 $491.99 25-49 $457.55 50-99 $423.11 100+ $393.59 **2.4mm Male to 2.92mm Male Miter Right Angle** VSWR 1.25:1 to 40 GHz **Model No:** PE91508	 PRICE 1-24 $377.99 25-49 $351.53 50-99 $325.07 100+ $302.39 **2.4mm Male to 2.92mm Female Miter Right Angle** VSWR 1.25:1 to 40 GHz **Model No:** PE91502
7	 PRICE 1-9 $369.99 10-24 $351.49 25-49 $332.99 50+ $318.19 **2.4mm Male to Full Detent Mini SMP Male** VSWR 1.25:1 to 50 GHz **Model No:** PE91121	 PRECISION PRICE 1-9 $261.99 10-24 $248.89 25-49 $235.79 50+ $225.31 **2.4mm Male to N Male** VSWR 1.15:1 to 18 GHz **Model No:** PE9504	 PRECISION PRICE 1-9 $293.99 10-24 $279.29 25-49 $264.59 50+ $252.83 **2.4mm Male to N Female** VSWR 1.15:1 to 18 GHz **Model No:** PE9501	 PRICE 1-4 $715.00 5-9 $679.25 10-24 $643.50 25+ $614.90 **2.4mm Female to 1.85mm Male** VSWR 1.3:1 to 50 GHz **Model No:** PE9673	 PRECISION PRICE 1-4 $421.99 5-9 $400.89 10-24 $379.79 25+ $362.91 **2.4mm Female to 1.85mm Male** VSWR 1.3:1 to 50 GHz **Model No:** PE91542

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $405.99 25-49 $377.57 50-99 $349.15 100+ $324.79 **2.4mm Female to 2.92mm Male Miter Right Angle** VSWR 1.25:1 to 40 GHz **Model No:** PE91526	 PRICE 1-24 $479.99 25-49 $446.39 50-99 $412.79 100+ $383.99 **2.4mm Female to 2.92mm Female Right Angle** VSWR 1.3:1 to 40 GHz **Model No:** PE91111	 PRICE 1-24 $423.99 25-49 $394.31 50-99 $364.63 100+ $339.19 **2.4mm Female to 2.92mm Female Miter Right Angle** VSWR 1.25:1 to 40 GHz **Model No:** PE91525	 PRICE 1-9 $355.99 10-24 $338.19 25-49 $320.39 50+ $306.15 **2.4mm Female to Full Detent Mini SMP Male** VSWR 1.25:1 to 50 GHz **Model No:** PE91122	 PRICE 1-9 $335.99 10-24 $319.19 25-49 $302.39 50+ $288.95 **2.4mm Female to Mini SMP Female** VSWR 1.25:1 to 50 GHz **Model No:** PE91123
2	 PRECISION PRICE 1-9 $285.99 10-24 $271.69 25-49 $257.39 50+ $245.95 **2.4mm Female to N Male** VSWR 1.15:1 to 18 GHz **Model No:** PE9503	 PRECISION PRICE 1-9 $267.99 10-24 $254.59 25-49 $241.19 50+ $230.47 **2.4mm Female to N Female** VSWR 1.15:1 to 18 GHz **Model No:** PE9502	 PRICE 1-9 $337.99 10-24 $321.09 25-49 $304.19 50+ $290.67 **2.4mm Female to SMP Male** VSWR 1.25:1 to 40 GHz **Model No:** PE91048	 PRICE 1-9 $391.99 10-24 $372.39 25-49 $352.79 50+ $337.11 **2.4mm Female to SMP Female** VSWR 1.25:1 to 40 GHz **Model No:** PE91055	***2.4mm NMD In-Series***
3	 PRICE 1-24 $455.99 25-49 $433.19 50-99 $410.39 100+ $392.15 **2.4mm NMD Female to 2.4mm Male** VSWR 1.25:1 to 50 GHz **Model No:** PE9973	 PRICE 1-24 $455.99 25-49 $433.19 50-99 $410.39 100+ $392.15 **2.4mm NMD Female to 2.92mm Female** VSWR 1.25:1 to 40 GHz **Model No:** PE9974	 PRICE 1-24 $455.99 25-49 $433.19 50-99 $410.39 100+ $392.15 **2.4mm NMD Female to 3.5mm Female** VSWR 1.25:1 to 34.5 GHz **Model No:** PE9978	 PRICE 1-24 $369.99 25-49 $351.49 50-99 $332.99 100+ $318.19 **2.4mm NMD Female to N Male** VSWR 1.15:1 to 18 GHz **Model No:** PE9985	 PRICE 1-24 $369.99 25-49 $351.49 50-99 $332.99 100+ $318.19 **2.4mm NMD Female to N Female** VSWR 1.15:1 to 18 GHz **Model No:** PE9982
4	 PRICE 1-24 $369.99 25-49 $351.49 50-99 $332.99 100+ $318.19 **2.4mm NMD Female to SMA Plug** VSWR 1.2:1 to 27 GHz **Model No:** PE9984	***2.4mm NMD Between Series***	 PRICE 1-9 $417.99 10-24 $397.09 25-49 $376.19 50+ $359.47 **2.4mm NMD Female to 2.4mm Female** Max. Freq. 50 GHz **Model No:** PE91145	 Ruggedized PRICE 1-9 $371.99 10-24 $353.39 25-49 $334.79 50+ $319.91 **2.4mm NMD Female to SMA Female** VSWR 1.2:1 to 27 GHz **Model No:** PE91146	***2.2-5 In-Series***
5	 Low PIM PRICE 1-24 $56.99 25-49 $54.14 50-99 $51.29 100+ $49.01 **2.2-5 Male to 2.2-5 Male** VSWR 1.25:1 to 8 GHz **Model No:** PE9792	 Low PIM PRICE 1-24 $56.99 25-49 $54.14 50-99 $51.29 100+ $49.01 **2.2-5 Female to 2.2-5 Female** VSWR 1.25:1 to 8 GHz **Model No:** PE9793	***2.92mm In-Series***	 PRICE 1-9 $227.99 10-24 $216.59 25-49 $205.19 50+ $196.07 **2.92mm Male to 2.92mm Male** VSWR 1.25:1 to 40 GHz **Model No:** PE9436	 PRICE 1-9 $369.99 10-24 $351.49 25-49 $332.99 50+ $318.19 **2.92mm Male to 2.92mm Male Miter Right Angle** VSWR 1.25:1 to 40 GHz **Model No:** PE91516
6	 PRICE 1-9 $235.99 10-24 $224.19 25-49 $212.39 50+ $202.95 **2.92mm Male to 2.92mm Female** VSWR 1.25:1 to 40 GHz **Model No:** PE9437	 PRICE 1-9 $267.99 10-24 $254.59 25-49 $241.19 50+ $230.47 **2.92mm Male to 2.92mm Female Miter Right Angle** VSWR 1.25:1 to 40 GHz **Model No:** PE91503	 PRICE 1-24 $88.99 25-49 $84.54 50-99 $80.09 100+ $76.53 **2.92mm Female to 2.92mm Female** VSWR 1.25:1 to 40 GHz **Model No:** PE91510	 PRICE 1-9 $245.99 10-24 $233.69 25-49 $221.39 50+ $211.55 **2.92mm Female to 2.92mm Female** VSWR 1.25:1 to 40 GHz **Model No:** PE9438	 PRICE 1-9 $373.99 10-24 $355.29 25-49 $336.59 50+ $321.63 **2.92mm Female to 2.92mm Female Miter Right Angle** VSWR 1.25:1 to 40 GHz **Model No:** PE91517
7	 PRICE 1-9 $155.99 10-24 $148.19 25-49 $140.39 50+ $134.15 **2.92mm Female to 2.92mm Female Bulkhead-Mounting Hole B02** VSWR 1.25:1 to 40 GHz **Model No:** PE9647	 PRICE 1-9 $275.99 10-24 $262.19 25-49 $248.39 50+ $237.35 **2.92mm Female to 2.92mm Female 4 Hole Flange** VSWR 1.35:1 to 40 GHz **Model No:** PE9648	 PRICE 1-24 $125.99 25-49 $120.95 50-99 $117.17 100+ $114.65 **2.92mm Female to 2.92mm Female 4 Hole Flange** VSWR 1.25:1 to 40 GHz **Model No:** PE91538	***2.92mm Between Series***	 PRICE 1-4 $665.00 5-9 $631.75 10-24 $598.50 25+ $571.90 **2.92mm Male to 1.85mm Male** VSWR 1.25:1 to 40 GHz **Model No:** PE9667

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-4 $670.00 5-9 $636.50 10-24 $603.00 25+ $576.20 **2.92mm Male to 1.85mm Female** VSWR 1.25:1 to 40 GHz **Model No:** PE9666	 PRICE 1-9 $297.99 10-24 $283.09 25-49 $268.19 50+ $256.27 **2.92mm Male to 2.4mm Male** VSWR 1.15:1 to 40 GHz **Model No:** PE91298	 PRICE 1-9 $209.99 10-24 $199.49 25-49 $188.99 50+ $180.59 **2.92mm Male to 2.4mm Male** VSWR 1.3:1 to 40 GHz **Model No:** PE9457	 PRICE 1 Call - - - **2.92mm Male to 2.4mm Female** VSWR 1.25:1 to 40 GHz **Model No:** PE91450	 PRICE 1-9 $173.99 10-24 $165.29 25-49 $156.59 50+ $149.63 **2.92mm Male to 2.4mm Female** VSWR 1.3:1 to 40 GHz **Model No:** PE9455
2	 PRICE 1-9 $383.99 10-24 $368.63 25-49 $357.11 50+ $349.43 **2.92mm Male to 2.92mm Female** **Radius Right Angle** VSWR 1.5:1 to 40 GHz **Model No:** PE91070	 PRICE 1-24 $305.99 25-49 $284.57 50-99 $263.15 100+ $244.79 **2.92mm Male to 3.5mm Male Right Angle** VSWR 1.25:1 to 34.5 GHz **Model No:** PE91165	 PRICE 1-9 $271.99 10-24 $258.39 25-49 $244.79 50+ $233.91 **2.92mm Male to 3.5mm Male Miter Right Angle** VSWR 1.25:1 to 34.5 GHz **Model No:** PE91522	 PRICE 1-24 $305.99 25-49 $284.57 50-99 $263.15 100+ $244.79 **2.92mm Male to 3.5mm Female Right Angle** VSWR 1.25:1 to 34.5 GHz **Model No:** PE91168	 PRICE 1-24 $271.99 25-49 $252.95 50-99 $233.91 100+ $217.59 **2.92mm Male to 3.5mm Female Miter Right Angle** VSWR 1.25:1 to 34.5 GHz **Model No:** PE91514
3	 PRICE 1-9 $560.00 10-24 $537.60 25-49 $520.80 50+ $509.60 **2.92mm Male to 7mm Sexless** VSWR 1.1:1 to 18 GHz **Model No:** PE9460	 PRICE 1-9 $283.99 10-24 $272.63 25-49 $264.11 50+ $258.43 **2.92mm Male to Mini SMP Male** VSWR 1.25:1 to 40 GHz **Model No:** PE91124	 PRICE 1-9 $283.99 10-24 $272.63 25-49 $264.11 50+ $258.43 **2.92mm Male to Smooth Bore Mini SMP Male** VSWR 1.4:1 to 40 GHz **Model No:** PE91125	 PRICE 1-9 $279.99 10-24 $268.79 25-49 $260.39 50+ $254.79 **2.92mm Male to Mini SMP Female** VSWR 1.4:1 to 40 GHz **Model No:** PE91126	 PRICE 1-9 $267.99 10-24 $254.59 25-49 $241.19 PRECISION 50+ $230.47 **2.92mm Male to N Male** VSWR 1.15:1 to 18 GHz **Model No:** PE9661
4	 PRICE 1-9 $381.99 10-24 $362.89 25-49 $343.79 PRECISION 50+ $328.51 **2.92mm Male to N Female** VSWR 1.15:1 to 18 GHz **Model No:** PE9662	 PRICE 1-4 $760.00 5-9 $722.00 10-24 $684.00 25+ $653.60 **2.92mm Female to 1.85mm Male** VSWR 1.25:1 to 40 GHz **Model No:** PE9665	 PRICE 1-9 $319.99 10-24 $303.99 25-49 $287.99 50+ $275.19 **2.92mm Female to 2.4mm Male** VSWR 1.25:1 to 40 GHz **Model No:** PE91451	 PRICE 1-24 $357.99 25-49 $340.09 50-99 $322.19 100+ $307.87 **2.92mm Female to 2.4mm Male** VSWR 1.15:1 to 40 GHz **Model No:** PE1281	 PRICE 1-9 $163.99 10-24 $155.79 25-49 $147.59 50+ $141.03 **2.92mm Female to 2.4mm Male** VSWR 1.25:1 to 40 GHz **Model No:** PE9454
5	 PRICE 1-24 $291.99 25-49 $271.55 50-99 $251.11 100+ $233.59 **2.92mm Female to 2.4mm Female** VSWR 1.2:1 to 40 GHz **Model No:** PE91499	 PRICE 1-9 $191.99 10-24 $182.39 25-49 $172.79 50+ $165.11 **2.92mm Female to 2.4mm Female** VSWR 1.3:1 to 40 GHz **Model No:** PE9456	 PRICE 1-9 $271.99 10-24 $258.39 25-49 $244.79 50+ $233.91 **2.92mm Female to 3.5mm Male Miter Right Angle** VSWR 1.25:1 to 34.5 GHz **Model No:** PE91520	 PRICE 1-9 $275.99 10-24 $262.19 25-49 $248.39 50+ $237.35 **2.92mm Female to 3.5mm Female** VSWR 1.25:1 to 34 GHz **Model No:** PE9660	 PRICE 1-24 $273.99 25-49 $254.81 50-99 $235.63 100+ $219.19 **2.92mm Female to 3.5mm Female Right Angle** VSWR 1.25:1 to 34.5 GHz **Model No:** PE91167
6	 PRICE 1-9 $251.99 10-24 $239.39 25-49 $226.79 50+ $216.71 **2.92mm Female to 3.5mm Female Miter Right Angle** VSWR 1.25:1 to 34.5 GHz **Model No:** PE91521	 PRICE 1-9 $625.00 10-24 $593.75 25-49 $562.50 PRECISION 50+ $537.50 **2.92mm Female to 7mm Sexless** VSWR 1.1:1 to 18 GHz **Model No:** PE9461	 PRICE 1-9 $283.99 10-24 $272.63 25-49 $264.11 50+ $258.43 **2.92mm Female to Full Detent Mini SMP Male** VSWR 1.35:1 to 40 GHz **Model No:** PE91127	 PRICE 1-9 $333.99 10-24 $320.63 25-49 $310.61 50+ $303.93 **2.92mm Female to Smooth Bore Mini SMP Male** VSWR 1.35:1 to 40 GHz **Model No:** PE91128	 PRICE 1-4 $930.00 5-9 $883.50 10-24 $837.00 25+ $799.80 **2.92mm Female to Mini SMP Female** VSWR 1.3:1 to 40 GHz **Model No:** PE9782
7	 PRICE 1-9 $273.99 10-24 $260.29 25-49 $246.59 PRECISION 50+ $235.63 **2.92mm Female to N Male** VSWR 1.15:1 to 18 GHz **Model No:** PE9663	 PRICE 1-9 $259.99 10-24 $246.99 25-49 $233.99 PRECISION 50+ $223.59 **2.92mm Female to N Female** VSWR 1.15:1 to 18 GHz **Model No:** PE9664	 PRICE 1-9 $251.99 10-24 $239.39 25-49 $226.79 50+ $216.71 **2.92mm Female to SMP Female** VSWR 1.25:1 to 40 GHz **Model No:** PE91060	 PRICE 1-9 $255.99 10-24 $243.19 25-49 $230.39 50+ $220.15 **2.92mm Female to SSMA Male** VSWR 1.25:1 to 40 GHz **Model No:** PE9768	***2.92mm NMD In-Series*** →

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $369.99 25-49 $351.49 50-99 $332.99 100+ $318.19 **2.92mm NMD Male to N Female** VSWR 1.15:1 to 18 GHz **Model No:** PE9986	 PRICE 1-24 $455.99 25-49 $433.19 50-99 $410.39 100+ $392.15 **2.92mm NMD Female to 2.92mm Male** VSWR 1.25:1 to 40 GHz **Model No:** PE9977	 PRICE 1-24 $455.99 25-49 $433.19 50-99 $410.39 100+ $392.15 **2.92mm NMD Female to 2.92mm Female** VSWR 1.25:1 to 40 GHz **Model No:** PE9975	 PRICE 1-24 $455.99 25-49 $433.19 50-99 $410.39 100+ $392.15 **2.92mm NMD Female to 3.5mm Female** VSWR 1.25:1 to 34.5 GHz **Model No:** PE9979	 PRICE 1-24 $369.99 25-49 $351.49 50-99 $332.99 100+ $318.19 **2.92mm NMD Female to N Female** VSWR 1.15:1 to 18 GHz **Model No:** PE9983
2	***2.92mm NMD Between Series*** →	 PRICE 1-9 $417.99 10-24 $397.09 25-49 $376.19 50+ $359.47 **2.92mm NMD Female to 2.4mm Female** VSWR 1.35:1 to 40 GHz **Model No:** PE91144	***3.5mm In-Series*** →	 PRICE 1-24 $325.99 25-49 $303.17 50-99 $280.35 100+ $260.79 **3.5mm Male to 3.5mm Male Right Angle** VSWR 1.25:1 to 34.5 GHz **Model No:** PE91169	 PRICE 1-9 $279.99 10-24 $265.99 25-49 $251.99 50+ $240.79 **3.5mm Male to 3.5mm Male Miter Right Angle** VSWR 1.35:1 to 34.5 GHz **Model No:** PE91515
3	 PRICE 1-9 $271.99 10-24 $258.39 25-49 $244.79 50+ $233.91 **3.5mm Male to 3.5mm Female Miter Right Angle** VSWR 1.35:1 to 34.5 GHz **Model No:** PE91523	 PRICE 1-9 $215.99 10-24 $205.19 25-49 $194.39 50+ $185.75 **3.5mm Female to 3.5mm Female** **Bulkhead-Mounting Hole B06** VSWR 1.25:1 to 34.5 GHz **Model No:** PE9678	 PRICE 1 $253.99 **3.5mm Female to 3.5mm Female** **Miter Right Angle** VSWR 1.35:1 to 34.5 GHz **Model No:** PE91528	***3.5mm Between Series*** →	 PRICE 1-9 $279.99 10-24 $265.99 25-49 $251.99 50+ $240.79 **3.5mm Male to 1.85mm Male** VSWR 1.3:1 to 34 GHz **Model No:** PE9746
4	 PRICE 1-9 $293.99 10-24 $279.29 25-49 $264.59 50+ $252.83 **3.5mm Male to 1.85mm Female** VSWR 1.3:1 to 34 GHz **Model No:** PE9745	 PRICE 1-9 $339.99 10-24 $322.99 25-49 $305.99 50+ $292.39 **3.5mm Male to 2.4mm Male** VSWR 1.15:1 to 34 GHz **Model No:** PE91294	 PRICE 1-9 $271.99 10-24 $258.39 25-49 $244.79 50+ $233.91 **3.5mm Male to 2.4mm Male** VSWR 1.25:1 to 34 GHz **Model No:** PE9649	 PRICE 1-24 $325.99 25-49 $303.17 50-99 $280.35 100+ $260.79 **3.5mm Male to 2.4mm Female** VSWR 1.3:1 to 34 GHz **Model No:** PE91452	 PRICE 1-9 $271.99 10-24 $258.39 25-49 $244.79 50+ $233.91 **3.5mm Male to 2.4mm Female** VSWR 1.25:1 to 34 GHz **Model No:** PE9651
5	 PRICE 1-9 $275.99 10-24 $262.19 25-49 $248.39 50+ $237.35 **3.5mm Male to 2.92mm Female** VSWR 1.25:1 to 34 GHz **Model No:** PE9658	 PRICE 1-9 $403.99 10-24 $383.79 25-49 $363.59 PRECISION 50+ $347.43 **3.5mm Male to 7mm Sexless** VSWR 1.15:1 to 18 GHz **Model No:** PE9326	 PRICE 1-9 $231.99 10-24 $220.39 25-49 $208.79 PRECISION 50+ $199.51 **3.5mm Male to N Male** VSWR 1.15:1 to 18 GHz **Model No:** PE9322	 PRICE 1-9 $267.99 10-24 $254.59 25-49 $241.19 50+ $230.47 **3.5mm Female to 1.85mm Female** VSWR 1.3:1 to 34 GHz **Model No:** PE9748	 PRICE 1-9 $275.99 10-24 $262.19 25-49 $248.39 50+ $237.35 **3.5mm Female to 2.4mm Male** VSWR 1.25:1 to 34 GHz **Model No:** PE9650
6	 PRICE 1 Call - - - **3.5mm Female to 2.4mm Female** VSWR 1.15:1 to 34 GHz **Model No:** PE91291	 PRICE 1-9 $243.99 10-24 $231.79 25-49 $219.59 50+ $209.83 **3.5mm Female to 2.4mm Female** VSWR 1.25:1 to 34 GHz **Model No:** PE9652	 PRICE 1-9 $231.99 10-24 $220.39 25-49 $208.79 50+ $199.51 **3.5mm Female to 2.4mm Female** VSWR 1.15:1 to 34.5 GHz **Model No:** PE91547	 PRICE 1-9 $273.99 10-24 $260.29 25-49 $246.59 50+ $235.63 **3.5mm Female to 2.92mm Male** VSWR 1.25:1 to 34.5 GHz **Model No:** PE9659	 PRICE 1-9 $545.00 10-24 $517.75 25-49 $490.50 PRECISION 50+ $468.70 **3.5mm Female to 7mm Sexless** VSWR 1.15:1 to 18 GHz **Model No:** PE9325
7	 PRICE 1-9 $363.99 10-24 $345.79 25-49 $327.59 PRECISION 50+ $313.03 **3.5mm Female to 7mm Sexless** VSWR 1.15:1 to 18 GHz **Model No:** PE91546	 PRICE 1-9 $227.99 10-24 $216.59 25-49 $205.19 PRECISION 50+ $196.07 **3.5mm Female to N Male** VSWR 1.15:1 to 18 GHz **Model No:** PE9321	 PRICE 1-9 $201.99 10-24 $191.89 25-49 $181.79 PRECISION 50+ $173.71 **3.5mm Female to N Female** VSWR 1.15:1 to 18 GHz **Model No:** PE9323	***3.5mm NMD In-Series*** →	 PRICE 1-24 $455.99 25-49 $433.19 50-99 $410.39 100+ $392.15 **3.5mm NMD Female to 2.92mm Male** VSWR 1.25:1 to 34.5 GHz **Model No:** PE9981

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $455.99 25-49 $433.19 50-99 $410.39 100+ $392.15 **3.5mm NMD Female to 2.92mm Female** VSWR 1.25:1 to 34.5 GHz **Model No:** PE9976	 PRICE 1-24 $455.99 25-49 $433.19 50-99 $410.39 100+ $392.15 **3.5mm NMD Female to 2.92mm Female** VSWR 1.25:1 to 34.5 GHz **Model No:** PE9980	 PRICE 1-24 $369.99 25-49 $351.49 50-99 $332.99 100+ $318.19 **3.5mm NMD Female to N Male** VSWR 1.15:1 to 18 GHz **Model No:** PE9987	***3.5mm NMD Between Series*** →	 PRICE 1-9 $417.99 10-24 $397.09 25-49 $376.19 50+ $359.47 **3.5mm NMD Female to 2.4mm Female** VSWR 1.25:1 to 33 GHz **Model No:** PE91148
2	 Ruggedized PRICE 1-9 $353.99 10-24 $336.29 25-49 $318.59 50+ $304.43 **3.5mm NMD Female to SMA Female** Max. Freq. 27 GHz **Model No:** PE91147	***7mm Between Series*** →	 PRECISION PRICE 1-9 $610.00 10-24 $585.60 25-49 $567.30 50+ $555.10 **7mm Sexless to BNC Male** VSWR 1.15:1 to 8 GHz **Model No:** PE9221	 PRECISION PRICE 1-9 $429.99 10-24 $408.49 25-49 $386.99 50+ $369.79 **7mm Sexless to BNC Female** VSWR 1.15:1 to 8 GHz **Model No:** PE9220	***4.1/9.5 Mini DIN In-Series*** →
3	 PRICE 1-24 $82.99 25-49 $78.84 50-99 $74.69 100+ $71.37 **4.1/9.5 Mini DIN Male to 4.1/9.5 Mini DIN Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91194	 PRICE 33-31 - 32-31 - 32-31 - 32+ - **4.1/9.5 Mini DIN Male to 4.1/9.5 Mini DIN Male** VSWR 1.3:1 to 6 GHz **Model No:** PE91231	 PRICE 1-24 $82.99 25-49 $78.84 50-99 $74.69 100+ $71.37 **4.1/9.5 Mini DIN Male to 4.1/9.5 Mini DIN Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91195	 PRICE 1-24 $36.99 25-49 $35.14 50-99 $33.29 100+ $31.81 **4.1/9.5 Mini DIN Female to 4.1/9.5 Mini DIN Female** VSWR 1.3:1 to 6 GHz **Model No:** PE91233	 PRICE 1-24 $99.99 25-49 $94.99 50-99 $89.99 100+ $85.99 **4.1/9.5 Mini DIN Female to 4.1/9.5 Mini DIN Female Bulkhead** VSWR 1.25:1 to 6 GHz **Model No:** PE91197
4	 PRICE 1-24 $39.39 25-49 $37.42 50-99 $35.45 100+ $33.88 **4.1/9.5 Mini DIN Female to 4.1/9.5 Mini DIN Female Bulkhead** VSWR 1.3:1 to 6 GHz **Model No:** PE91234	***4.1/9.5 Mini DIN Between Series*** →	 PRICE 1-24 $71.99 25-49 $68.39 50-99 $64.79 100+ $61.91 **4.1/9.5 Mini DIN Male to N Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91216	 Low PIM PRICE 1-24 $75.99 25-49 $72.19 50-99 $68.39 100+ $65.35 **4.1/9.5 Mini DIN Male to N Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91092	 PRICE 1-24 $78.99 25-49 $75.04 50-99 $71.09 100+ $67.93 **4.1/9.5 Mini DIN Male to N Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91217
5	 PRICE 1-24 $73.99 25-49 $70.29 50-99 $66.59 100+ $63.63 **4.1/9.5 Mini DIN Male to N Female** VSWR 1.3:1 to 6 GHz **Model No:** PE91254	 Low PIM PRICE 1-24 $73.99 25-49 $70.29 50-99 $66.59 100+ $63.63 **4.1/9.5 Mini DIN Male to N Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91093	 PRICE 1-24 $71.99 25-49 $68.39 50-99 $64.79 100+ $61.91 **4.1/9.5 Mini DIN Female to N Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91219	 PRICE 1-24 $87.99 25-49 $83.59 50-99 $79.19 100+ $75.67 **4.1/9.5 Mini DIN Female to N Male** VSWR 1.3:1 to 6 GHz **Model No:** PE91256	 Low PIM PRICE 1-24 $75.99 25-49 $72.19 50-99 $68.39 100+ $65.35 **4.1/9.5 Mini DIN Female to N Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91094
6	 PRICE 1-24 $69.99 25-49 $66.49 50-99 $62.99 100+ $60.19 **4.1/9.5 Mini DIN Female to N Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91218	 PRICE 1-24 $76.99 25-49 $73.14 50-99 $69.29 100+ $66.21 **4.1/9.5 Mini DIN Female to N Female** VSWR 1.3:1 to 6 GHz **Model No:** PE91255	 Low PIM PRICE 1-24 $75.99 25-49 $72.19 50-99 $68.39 100+ $65.35 **4.1/9.5 Mini DIN Female to N Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91095	***4.3 Non Constant In-Series*** →	 Low PIM PRICE 1-24 $45.19 25-49 $42.93 50-99 $40.67 100+ $38.86 **4.3-10 Male to 4.3-10 Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91466
7	 Low PIM PRICE 1-24 $101.99 25-49 $96.89 50-99 $91.79 100+ $87.71 **4.3-10 Male to 4.3-10 Male** VSWR 1.08:1 to 6 GHz **Model No:** PE91385	 Low PIM PRICE 1-24 $50.99 25-49 $48.44 50-99 $45.89 100+ $43.85 **4.3-10 Male to 4.3-10 Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91465	 Low PIM PRICE 1-24 $101.99 25-49 $96.89 50-99 $91.79 100+ $87.71 **4.3-10 Male to 4.3-10 Female Right Angle** VSWR 1.2:1 to 3 GHz **Model No:** PE91467	 Low PIM PRICE 1-24 $103.99 25-49 $99.83 50-99 $96.71 100+ $94.63 **4.3-10 Male to 4.3-10 Female** VSWR 1.08:1 to 6 GHz **Model No:** PE91387	 Low PIM PRICE 1-24 $50.99 25-49 $48.44 50-99 $45.89 100+ $43.85 **4.3-10 Female to 4.3-10 Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91464

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 Low PIM PRICE 1-24 $105.99 25-49 $100.69 50-99 $95.39 100+ $91.15 **4.3-10 Female to 4.3-10 Female** VSWR 1.08:1 to 6 GHz **Model No:** PE91386	***4.3 Non Constant Between Series*** →	 Low PIM PRICE 1-24 $45.19 25-49 $42.93 50-99 $40.67 100+ $38.86 **4.3-10 Male to N Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91476	 Low PIM PRICE 1-24 $61.99 25-49 $58.89 50-99 $55.79 100+ $53.31 **QD 4.3-10 Male to N Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91480	 Low PIM PRICE 1-24 $45.19 25-49 $42.93 50-99 $40.67 100+ $38.86 **4.3-10 Male to N Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91474
2	 Low PIM PRICE 1-24 $45.19 25-49 $42.93 50-99 $40.67 100+ $38.86 **4.3-10 Male to N Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91477	 Low PIM PRICE 1-24 $59.99 25-49 $56.99 50-99 $53.99 100+ $51.59 **QD 4.3-10 Male to N Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91478	 Low PIM PRICE 1-24 $71.99 25-49 $68.39 50-99 $64.79 100+ $61.91 **4.3-10 Male to N Female Right Angle** VSWR 1.25:1 to 6 GHz **Model No:** PE91483	 Low PIM PRICE 1-24 $107.99 25-49 $102.59 50-99 $97.19 100+ $92.87 **4.3-10 Male to N Female** VSWR 1.08:1 to 6 GHz **Model No:** PE91389	 Low PIM PRICE 1-24 $40.79 25-49 $38.75 50-99 $36.71 100+ $35.08 **4.3-10 Male to SMA Female** VSWR 1.15:1 to 6 GHz **Model No:** PE91484
3	 Low PIM PRICE 1-24 $52.99 25-49 $50.34 50-99 $47.69 100+ $45.57 **4.3-10 Female to N Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91479	 Low PIM PRICE 1-24 $49.99 25-49 $47.49 50-99 $44.99 100+ $42.99 **QD 4.3-10 Female to N Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91481	 Low PIM PRICE 1-24 $46.19 25-49 $43.88 50-99 $41.57 100+ $39.72 **4.3-10 Female to N Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91475	 Low PIM PRICE 1-24 $49.79 25-49 $47.30 50-99 $44.81 100+ $42.82 **QD 4.3-10 Female to N Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91482	***7/16 DIN In-Series*** →
4	 PRICE 1-24 $109.99 25-49 $104.49 50-99 $98.99 100+ $94.59 **7/16 DIN Male to 7/16 DIN Male** VSWR 1.15:1 to 6 GHz **Model No:** PE91190	 PRICE 1-24 $113.99 25-49 $108.29 50-99 $102.59 100+ $98.03 **7/16 DIN Male to 7/16 DIN Male** VSWR 1.25:1 to 6 GHz **Model No:** PE91227	 Low PIM PRICE 1-9 $165.99 10-24 $157.69 25-49 $149.39 50+ $142.75 **7/16 DIN Male to 7/16 DIN Male** Max. Freq. 8 GHz **Model No:** PE91039	 PRICE 1-24 $83.99 25-49 $79.79 50-99 $75.59 100+ $72.23 **7/16 DIN Male to 7/16 DIN Female** VSWR 1.15:1 to 6 GHz **Model No:** PE91191	 PRICE 1-24 $85.99 25-49 $81.69 50-99 $77.39 100+ $73.95 **7/16 DIN Male to 7/16 DIN Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91228
5	 PRICE 1 Call - - - **7/16 DIN Male to 7/16 DIN Female** VSWR 1.35:1 to 7.5 GHz **Model No:** PE91027	 Low PIM PRICE 1-9 $135.99 10-24 $129.19 25-49 $122.39 50+ $116.95 **7/16 DIN Male to 7/16 DIN Female** Max. Freq. 8 GHz **Model No:** PE91028	 PRICE 1-24 $103.99 25-49 $98.79 50-99 $93.59 100+ $89.43 **7/16 DIN Male to 7/16 DIN Female Right Angle** VSWR 1.25:1 to 6 GHz **Model No:** PE91117	 PRICE 1-9 $325.99 10-24 $309.69 25-49 $293.39 50+ $280.35 **7/16 DIN Female to 7/16 DIN Male Tee** Max. Freq. 7.5 GHz **Model No:** PE9557	 PRICE 1-24 $92.99 25-49 $88.34 50-99 $83.69 100+ $79.97 **7/16 DIN Female to 7/16 DIN Female** VSWR 1.15:1 to 6 GHz **Model No:** PE91192
6	 PRICE 1-24 $121.99 25-49 $115.89 50-99 $109.79 100+ $104.91 **7/16 DIN Female to 7/16 DIN Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91229	 Low PIM PRICE 1-9 $135.99 10-24 $129.19 25-49 $122.39 50+ $116.95 **7/16 DIN Female to 7/16 DIN Female** Max. Freq. 8 GHz **Model No:** PE91029	 PRICE 1-9 $151.99 10-24 $144.39 25-49 $136.79 50+ $130.71 **7/16 DIN Female to 7/16 DIN Female** **Model No:** PE9409	 PRICE 1-9 $341.99 10-24 $324.89 25-49 $307.79 50+ $294.11 **7/16 DIN Female to 7/16 DIN Female Tee** **Model No:** PE9556	 Low PIM PRICE 1-9 $179.99 10-24 $170.99 25-49 $161.99 50+ $154.79 **7/16 DIN Female to 7/16 DIN Female Bulkhead** Max. Freq. 8 GHz **Model No:** PE91038
7	 PRICE 1-9 $323.99 10-24 $307.79 25-49 $291.59 50+ $278.63 **7/16 DIN Female to 7/16 DIN Female Bulkhead** **Model No:** PE9414	 PRICE 1-24 $141.99 25-49 $134.89 50-99 $127.79 100+ $122.11 **7/16 DIN Female to 7/16 DIN Female Bulkhead** VSWR 1.25:1 to 6 GHz **Model No:** PE91193	 PRICE 1-24 $119.99 25-49 $113.99 50-99 $107.99 100+ $103.19 **7/16 DIN Female to 7/16 DIN Female Bulkhead** VSWR 1.25:1 to 6 GHz **Model No:** PE91230	***7/16 DIN Between Series*** →	 Low PIM PRICE 1-24 $56.99 25-49 $54.14 50-99 $51.29 100+ $49.01 **7/16 DIN Male to 2.2-5 Male** VSWR 1.25:1 to 8 GHz **Model No:** PE9798

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 Low PIM PRICE 1-24 $56.99 25-49 $54.14 50-99 $51.29 100+ $49.01 **7/16 DIN Male to 2.2-5 Female** VSWR 1.25:1 to 8 GHz **Model No: PE9799**	 PRICE 1 Call - - - **7/16 DIN Male to 4.1/9.5 Mini DIN Male** VSWR 1.25:1 to 6 GHz **Model No: PE91206**	 PRICE 1-24 $49.59 25-49 $47.11 50-99 $44.63 100+ $42.65 **7/16 DIN Male to 4.1/9.5 Mini DIN Male** VSWR 1.3:1 to 6 GHz **Model No: PE91243**	 Low PIM PRICE 1-24 $98.99 25-49 $94.04 50-99 $89.09 100+ $85.13 **7/16 DIN Male to 4.1/9.5 Mini DIN Male** VSWR 1.25:1 to 6 GHz **Model No: PE91088**	 PRICE 1-24 $74.99 25-49 $71.24 50-99 $67.49 100+ $64.49 **7/16 DIN Male to 4.1/9.5 Mini DIN Female** VSWR 1.25:1 to 6 GHz **Model No: PE91207**
2	 PRICE 1-24 $45.99 25-49 $43.69 50-99 $41.39 100+ $39.55 **7/16 DIN Male to 4.1/9.5 Mini DIN Female** VSWR 1.25:1 to 6 GHz **Model No: PE91244**	 Low PIM PRICE 1-24 $47.19 25-49 $44.83 50-99 $42.47 100+ $40.58 **7/16 DIN Male to 4.3-10 Male** VSWR 1.25:1 to 6 GHz **Model No: PE91468**	 Low PIM PRICE 1-24 $50.99 25-49 $48.44 50-99 $45.89 100+ $43.85 **7/16 DIN Male to 4.3-10 Female** VSWR 1.25:1 to 6 GHz **Model No: PE91469**	 Low PIM PRICE 1-24 $87.99 25-49 $83.59 50-99 $79.19 100+ $75.67 **7/16 DIN Male to 4.3-10 Female** VSWR 1.08:1 to 6 GHz **Model No: PE91390**	 PRICE 1-9 $185.99 10-24 $176.69 25-49 $167.39 50+ $159.95 **7/16 DIN Male to HN Female** **Model No: PE9558**
3	 PRICE 1-24 $82.99 25-49 $78.84 50-99 $74.69 100+ $71.37 **7/16 DIN Male to N Male** VSWR 1.15:1 to 6 GHz **Model No: PE91211**	 PRICE 1-24 $103.99 25-49 $98.79 50-99 $93.59 100+ $89.43 **7/16 DIN Male to N Male** VSWR 1.25:1 to 6 GHz **Model No: PE91248**	 PRICE 1-24 $79.99 25-49 $75.99 50-99 $71.99 100+ $68.79 **7/16 DIN Male to N Female** VSWR 1.15:1 to 6 GHz **Model No: PE91212**	 PRICE 1-24 $60.99 25-49 $57.94 50-99 $54.89 100+ $52.45 **7/16 DIN Male to N Female** VSWR 1.25:1 to 6 GHz **Model No: PE91249**	 PRICE 1-9 $227.99 10-24 $216.59 25-49 $205.19 50+ $196.07 **7/16 DIN Male to SC Female** VSWR 1.25:1 to 7.5 GHz **Model No: PE91444**
4	 PRICE 1-24 $86.99 25-49 $82.64 50-99 $78.29 100+ $74.81 **7/16 DIN Female to 4.1/9.5 Mini DIN Male** VSWR 1.25:1 to 6 GHz **Model No: PE91209**	 PRICE 1-24 $43.19 25-49 $41.03 50-99 $38.87 100+ $37.14 **7/16 DIN Female to 4.1/9.5 Mini DIN Male** VSWR 1.25:1 to 6 GHz **Model No: PE91246**	 Low PIM PRICE 1-24 $98.99 25-49 $94.04 50-99 $89.09 100+ $85.13 **7/16 DIN Female to 4.1/9.5 Mini DIN Male** VSWR 1.25:1 to 6 GHz **Model No: PE91090**	 PRICE 1-24 $78.99 25-49 $75.04 50-99 $71.09 100+ $67.93 **7/16 DIN Female to 4.1/9.5 Mini DIN Female** VSWR 1.25:1 to 6 GHz **Model No: PE91208**	 PRICE 1-24 $41.79 25-49 $39.70 50-99 $37.61 100+ $35.94 **7/16 DIN Female to 4.1/9.5 Mini DIN Female** VSWR 1.35:1 to 6 GHz **Model No: PE91245**
5	 Low PIM PRICE 1-24 $98.99 25-49 $94.04 50-99 $89.09 100+ $85.13 **7/16 DIN Female to 4.1/9.5 Mini DIN Female** VSWR 1.25:1 to 6 GHz **Model No: PE91091**	 PRICE 1 Call - - - **7/16 DIN Female to 4.1/9.5 Mini DIN Female Bulkhead** VSWR 1.3:1 to 6 GHz **Model No: PE91247**	 Low PIM PRICE 1-24 $49.99 25-49 $47.49 50-99 $44.99 100+ $42.99 **7/16 DIN Female to 4.3-10 Male** VSWR 1.2:1 to 6 GHz **Model No: PE91470**	 Low PIM PRICE 1-24 $68.99 25-49 $65.54 50-99 $62.09 100+ $59.33 **7/16 DIN Female to QD 4.3-10 Male** VSWR 1.2:1 to 6 GHz **Model No: PE91472**	 Low PIM PRICE 1-9 $141.99 10-24 $134.89 25-49 $127.79 50+ $122.11 **7/16 DIN Female to 4.3-10 Male** VSWR 1.08:1 to 6 GHz **Model No: PE91391**
6	 Low PIM PRICE 1-24 $50.99 25-49 $48.44 50-99 $45.89 100+ $43.85 **7/16 DIN Female to 4.3-10 Female** VSWR 1.25:1 to 6 GHz **Model No: PE91471**	 Low PIM PRICE 1-24 $51.99 25-49 $49.39 50-99 $46.79 100+ $44.71 **7/16 DIN Female to QD 4.3-10 Female** VSWR 1.2:1 to 6 GHz **Model No: PE91473**	 Low PIM PRICE 1-9 $107.99 10-24 $102.59 25-49 $99.35 50+ $96.11 **7/16 DIN Female to 7/16 DIN Female Bulkhead** Max. Freq. 6 GHz **Model No: PE1280**	 PRICE 1-9 $203.99 10-24 $193.79 25-49 $183.59 50+ $175.43 **7/16 DIN Female to HN Male** **Model No: PE9559**	 PRICE 1-24 $61.99 25-49 $58.89 50-99 $55.79 100+ $53.31 **7/16 DIN Female to N Male** VSWR 1.25:1 to 6 GHz **Model No: PE91251**
7	 PRICE 1-24 $76.99 25-49 $73.14 50-99 $69.29 100+ $66.21 **7/16 DIN Female to N Female** VSWR 1.15:1 to 6 GHz **Model No: PE91213**	 PRICE 1-24 $62.99 25-49 $59.84 50-99 $56.69 100+ $54.17 **7/16 DIN Female to N Female** VSWR 1.25:1 to 6 GHz **Model No: PE91250**	 PRICE 1-24 $107.99 25-49 $102.59 50-99 $97.19 100+ $92.87 **7/16 DIN Female to N Female Bulkhead** VSWR 1.15:1 to 6 GHz **Model No: PE91215**	 PRICE 1-24 $56.99 25-49 $54.14 50-99 $51.29 100+ $49.01 **7/16 DIN Female to N Female Bulkhead** VSWR 1.25:1 to 6 GHz **Model No: PE91252**	***10-32 In-Series***

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $57.99 25-49 $55.09 50-99 $52.19 100+ $49.87 **10-32 Female to 10-32 Female** **Model No:** PE9756	 PRICE 1-24 $83.99 25-49 $79.79 50-99 $75.59 100+ $72.23 **10-32 Female to 10-32 Female Bulkhead** **Model No:** PE9757	***10-32 Between Series*** →	 PRICE 1-24 $107.99 25-49 $102.59 50-99 $97.19 100+ $92.87 **10-32 Male to BNC Male** **Model No:** PE9751	 PRICE 1-24 $96.99 25-49 $92.14 50-99 $87.29 100+ $83.41 **10-32 Male to BNC Female** **Model No:** PE9753
2	 PRICE 1-24 $125.99 25-49 $119.69 50-99 $113.39 100+ $108.35 **10-32 Male to BNC Female Bulkhead** **Model No:** PE9755	 PRICE 1-24 $71.99 25-49 $68.39 50-99 $64.79 100+ $61.91 **10-32 Female to BNC Male** **Model No:** PE9750	 PRICE 1-24 $87.99 25-49 $83.59 50-99 $79.19 100+ $75.67 **10-32 Female to BNC Female** **Model No:** PE9752	 PRICE 1-24 $81.99 25-49 $77.89 50-99 $73.79 100+ $70.51 **10-32 Female to BNC Female Bulkhead** **Model No:** PE9754	***BMA In-Series*** →
3	 PRICE 1-24 $68.99 25-49 $65.54 50-99 $62.09 100+ $59.33 **Slide-On BMA Jack to Slide-On BMA Jack** VSWR 1.2:1 to 22 GHz **Model No:** PE91395	***BMA Between Series*** →	 PRICE 1-9 $129.99 10-24 $123.49 25-49 $116.99 50+ $111.79 **Slide-On BMA Plug to SMA Male** VSWR 1.15:1 to 18 GHz **Model No:** PE91396	 PRICE 1-24 $129.99 25-49 $123.49 50-99 $116.99 100+ $111.79 **Slide-On BMA Plug to SMA Male Bulkhead** VSWR 1.15:1 to 18 GHz **Model No:** PE91401	 PRICE 1-9 $125.99 10-24 $119.69 25-49 $113.39 50+ $108.35 **Slide-On BMA Plug to SMA Female** VSWR 1.15:1 to 18 GHz **Model No:** PE91398
4	 PRICE 1-9 $149.99 10-24 $142.49 25-49 $134.99 50+ $128.99 **Slide-On BMA Plug to SMA Female Bulkhead** VSWR 1.15:1 to 18 GHz **Model No:** PE91402	 PRICE 1-9 $181.99 10-24 $172.89 25-49 $163.79 50+ $156.51 **Slide-On BMA Jack to SMA Female** VSWR 1.25:1 to 18 GHz **Model No:** PE91400	 PRICE 1-9 $165.99 10-24 $157.69 25-49 $149.39 50+ $142.75 **Slide-On BMA Jack to SMA Female 2 Hole Flange** VSWR 1.25:1 to 18 GHz **Model No:** PE91399	***BNC In-Series*** →	 PRICE 1-24 $28.59 25-49 $27.16 50-99 $25.73 100+ $24.59 **BNC Male to BNC Male** VSWR 1.3:1 to 1,000 MHz **Model No:** PE9000
5	 PRICE 1-24 $72.99 25-49 $69.34 50-99 $65.69 100+ $62.77 **BNC Male to BNC Male Right Angle** Max. Freq. 4 GHz **Model No:** PE9758	 PRICE 1-24 $44.99 25-49 $42.74 50-99 $40.49 100+ $38.69 **BNC Male to BNC Female** VSWR 1.3:1 to 4 GHz **Model No:** PE9269	 PRICE 1-24 $35.19 25-49 $33.43 50-99 $31.67 100+ $30.26 **BNC Male to BNC Female Right Angle** Max. Freq. 4 GHz **Model No:** PE9085	 PRICE 1-24 $63.99 25-49 $60.79 50-99 $57.59 100+ $55.03 **BNC Male to BNC Female Tee** VSWR 2.1:1 to 100 MHz **Model No:** PE9174	 PRICE 1-24 $64.99 25-49 $61.74 50-99 $58.49 100+ $55.89 **BNC Male to BNC Female Tee** Max. Freq. 100 MHz **Model No:** PE9484
6	 PRICE 1-24 $28.59 25-49 $27.16 50-99 $25.73 100+ $24.59 **BNC Female to BNC Male Tee** Max. Freq. 4 GHz **Model No:** PE9001	 PRICE 1-24 $16.39 25-49 $15.57 50-99 $14.75 100+ $14.10 **BNC Female to BNC Female** VSWR 1.3:1 to 4 GHz **Model No:** PE9084	 PRICE 1-24 $32.59 25-49 $30.96 50-99 $29.33 100+ $28.03 **BNC Female to BNC Female Tee** VSWR 2.1:1 to 100 MHz **Model No:** PE9003	 PRICE 1-24 $117.99 25-49 $112.09 50-99 $106.19 100+ $101.47 **BNC Female to BNC Female Bulkhead-Mounting Hole B06** **Model No:** PE9420	 PRICE 1-24 $36.59 25-49 $34.76 50-99 $32.93 100+ $31.47 **BNC Female to BNC Female Bulkhead** VSWR 1.5:1 to 4 GHz **Model No:** PE9093
7	 PRICE 1-24 $36.99 25-49 $35.14 50-99 $33.29 100+ $31.81 **BNC Female to BNC Female Bulkhead** VSWR 1.5:1 to 4 GHz **Model No:** PE9172	 PRICE 1-24 $25.39 25-49 $24.12 50-99 $22.85 100+ $21.84 **BNC Female to BNC Female 4 Hole Flange-Mounting Hole A03** VSWR 1.3:1 to 4 GHz **Model No:** PE9106	***BNC Between Series*** →	 PRICE 1-24 $31.99 25-49 $30.39 50-99 $28.79 100+ $27.51 **BNC Male to Double Banana Binding Post Jack** **Model No:** PE9011	 PRICE 1-24 $105.99 25-49 $100.69 50-99 $95.39 100+ $91.15 **BNC Male to BNC Triax Female** **Model No:** PE91104

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $125.99 25-49 $119.69 50-99 $113.39 100+ $108.35 **BNC Male to C Male** **Model No:** PE9536	 PRICE 1-24 $73.99 25-49 $70.29 50-99 $66.59 100+ $63.63 **BNC Male to C Female** **Model No:** PE9109	 PRICE 1-24 $31.19 25-49 $29.63 50-99 $28.07 100+ $26.82 **BNC Male to 75 Ohm F Male** **Model No:** PE9152	 PRICE 1-24 $38.19 25-49 $36.28 50-99 $34.37 100+ $32.84 **BNC Male to 75 Ohm F Female** VSWR 1.5:1 to 300 MHz **Model No:** PE9150	 PRICE 1-9 $141.99 10-24 $134.89 25-49 $127.79 50+ $122.11 **BNC Male to MHV Female** **Model No:** PE9406
2	 PRICE 1-24 $27.59 25-49 $26.21 50-99 $24.83 100+ $23.73 **BNC Male to 75 Ohm Push-On RCA Jack** Max. Freq. 250 MHz **Model No:** PE9171	 PRICE 1-24 $87.99 25-49 $83.59 50-99 $79.19 100+ $75.67 **BNC Male to 75 Ohm SMB Plug** **Model No:** PE9230	 PRICE 1-24 $85.99 25-49 $81.69 50-99 $77.39 100+ $73.95 **BNC Male to 75 Ohm SMC Plug** **Model No:** PE9234	 PRICE 1-24 $115.99 25-49 $110.19 50-99 $104.39 100+ $99.75 **BNC Male to 75 Ohm SMC Jack** **Model No:** PE91044	 PRICE 1-24 $51.99 25-49 $49.39 50-99 $46.79 100+ $44.71 **BNC Female to C Male** VSWR 1.3:1 to 4 GHz **Model No:** PE9087
3	 PRICE 1-24 $125.99 25-49 $119.69 50-99 $113.39 100+ $108.35 **BNC Female to C Female** **Model No:** PE9537	 PRICE 1-24 $125.99 25-49 $119.69 50-99 $113.39 100+ $108.35 **BNC Female to C Female Bulkhead-Mounting Hole G01** **Model No:** PE9204	 PRICE 1-24 $32.39 25-49 $30.77 50-99 $29.15 100+ $27.86 **BNC Female to 75 Ohm F Male** VSWR 1.3:1 to 500 MHz **Model No:** PE9151	 PRICE 1-24 $24.19 25-49 $22.98 50-99 $21.77 100+ $20.80 **BNC Female to 75 Ohm F Female** Max. Freq. 1,000 MHz **Model No:** PE9153	 PRICE 1-24 $24.59 25-49 $23.36 50-99 $22.13 100+ $21.15 **BNC Female to 75 Ohm RCA Plug** Max. Freq. 250 MHz **Model No:** PE9158
4	 PRICE 1-24 $17.79 25-49 $16.90 50-99 $16.01 100+ $15.30 **BNC Female to 75 Ohm RCA Jack** Max. Freq. 250 MHz **Model No:** PE9015	 PRICE 1-24 $76.99 25-49 $73.14 50-99 $69.29 100+ $66.21 **BNC Female to 75 Ohm SMB Jack** VSWR 1.2:1 to 4 GHz **Model No:** PE9231	 PRICE 1-24 $103.99 25-49 $98.79 50-99 $93.59 100+ $89.43 **BNC Female to 75 Ohm SMC Plug** **Model No:** PE9236	***Reverse Polarity BNC In-Series***	 PRICE 1-24 $52.99 25-49 $50.34 50-99 $47.69 100+ $45.57 **BNC Male to Rev. Pol. BNC Female** **Model No:** PE9530
5	 PRICE 1-24 $71.99 25-49 $68.39 50-99 $64.79 100+ $61.91 **BNC Female to Rev. Pol. BNC Male** **Model No:** PE9529	***C In-Series***	 PRICE 1-24 $145.99 25-49 $138.69 50-99 $131.39 100+ $125.55 **C Male to C Male** **Model No:** PE9300	 PRICE 1-24 $115.99 25-49 $110.19 50-99 $104.39 100+ $99.75 **C Male to C Female Right Angle** **Model No:** PE9293	 PRICE 1-24 $127.99 25-49 $121.59 50-99 $115.19 100+ $110.07 **C Female to C Male Tee** **Model No:** PE9207
6	 PRICE 1-24 $62.99 25-49 $59.84 50-99 $56.69 100+ $54.17 **C Female to C Female** **Model No:** PE9208	 PRICE 1-24 $149.99 25-49 $142.49 50-99 $134.99 100+ $128.99 **C Female to C Female Tee** **Model No:** PE9294	 PRICE 1-24 $147.99 25-49 $140.59 50-99 $133.19 100+ $127.27 **C Female to C Female Bulkhead-Mounting Hole B07** **Model No:** PE9186	***D-Sub In-Series***	 PRICE 1-24 $63.99 25-49 $60.79 50-99 $57.59 100+ $55.03 **D-Sub Plug to D-Sub Plug** **Model No:** PE9688
7	 PRICE 1-24 $62.99 25-49 $59.84 50-99 $56.69 100+ $54.17 **D-Sub Plug to D-Sub Receptacle** **Model No:** PE9687	 PRICE 1-24 $89.99 25-49 $85.49 50-99 $80.99 100+ $77.39 **D-Sub Receptacle to D-Sub Receptacle** **Model No:** PE9689	***FME In-Series***	 PRICE 1-24 $26.99 25-49 $25.64 50-99 $24.29 100+ $23.21 **FME Plug to FME Plug** **Model No:** PE9696	***FME Between Series***

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $26.99 25-49 $25.64 50-99 $24.29 100+ $23.21 **FME Plug to BNC Male** **Model No:** PE9697	 PRICE 1-24 $27.59 25-49 $26.21 50-99 $24.83 100+ $23.73 **FME Plug to BNC Male Right Angle** **Model No:** PE9698	 PRICE 1-24 $26.99 25-49 $25.64 50-99 $24.29 100+ $23.21 **FME Jack to BNC Male** **Model No:** PE9711	 PRICE 1-24 $21.59 25-49 $20.51 50-99 $19.43 100+ $18.57 **FME Jack to BNC Female** **Model No:** PE9712	***GR874 In-Series*** →
2	 PRICE 1-9 $425.99 10-24 $404.69 25-49 $383.39 50+ $366.35 **GR874 Sexless to GR874 Sexless Right Angle** **Model No:** PE9286	 PRICE 1-9 $467.99 10-24 $444.59 25-49 $421.19 50+ $402.47 **GR874 Sexless to GR874 Sexless Tee** **Model No:** PE9285	***GR874 Between Series*** →	 PRICE 1-9 $205.99 10-24 $195.69 25-49 $185.39 50+ $177.15 **GR874 Sexless to BNC Male** **Model No:** PE9223	 PRICE 1-9 $213.99 10-24 $203.29 25-49 $192.59 50+ $184.03 **GR874 Sexless to C Female** **Model No:** PE9301
3	***HN In-Series*** →	 PRICE 1-24 $80.99 25-49 $76.94 50-99 $72.89 100+ $69.65 **HN Male to HN Male** VSWR 1.4:1 to 3 GHz **Model No:** PE9210	 PRICE 1-9 $195.99 10-24 $186.19 25-49 $176.39 50+ $168.55 **HN Male to HN Male Right Angle** **Model No:** PE9577	 PRICE 1-24 $123.99 25-49 $117.79 50-99 $111.59 100+ $106.63 **HN Male to HN Female** **Model No:** PE9576	 PRICE 1-24 $83.99 25-49 $79.79 50-99 $75.59 100+ $72.23 **HN Male to HN Female Right Angle** VSWR 1.5:1 to 3 GHz **Model No:** PE9205
4	 PRICE 1-9 $243.99 10-24 $231.79 25-49 $219.59 50+ $209.83 **HN Male to HN Female Tee** **Model No:** PE9578	 PRICE 1-9 $203.99 10-24 $193.79 25-49 $183.59 50+ $175.43 **HN Female to HN Male Tee** **Model No:** PE9575	 PRICE 1-24 $73.99 25-49 $70.29 50-99 $66.59 100+ $63.63 **HN Female to HN Female** **Model No:** PE9580	 PRICE 1-9 $179.99 10-24 $170.99 25-49 $161.99 50+ $154.79 **HN Female to HN Female Tee** **Model No:** PE9574	 PRICE 1-24 $93.99 25-49 $89.29 50-99 $84.59 100+ $80.83 **HN Female to HN Female Bulkhead-Mounting Hole G03** VSWR 1.3:1 to 2 GHz **Model No:** PE9193
5	***HN Between Series*** →	 PRICE 1-24 $119.99 25-49 $113.99 50-99 $107.99 100+ $103.19 **HN Male to BNC Male** **Model No:** PE9567	 PRICE 1-24 $80.99 25-49 $76.94 50-99 $72.89 100+ $69.65 **HN Male to BNC Female** VSWR 1.5:1 to 4 GHz **Model No:** PE9126	 PRICE 1-24 $129.99 25-49 $123.49 50-99 $116.99 100+ $111.79 **HN Male to C Male** Max. Freq. 4 GHz **Model No:** PE9579	 PRICE 1-24 $101.99 25-49 $96.89 50-99 $91.79 100+ $87.71 **HN Male to C Female** **Model No:** PE9296
6	 PRICE 1-9 $265.99 10-24 $252.69 25-49 $239.39 50+ $228.75 **HN Male to GR874 Sexless** **Model No:** PE9386	 PRICE 1-9 $179.99 10-24 $170.99 25-49 $161.99 50+ $154.79 **HN Male to MHV Female** **Model No:** PE9264	 PRICE 1-24 $85.99 25-49 $81.69 50-99 $77.39 100+ $73.95 **HN Female to BNC Male** **Model No:** PE9129	 PRICE 1-24 $153.99 25-49 $146.29 50-99 $138.59 100+ $132.43 **HN Female to C Male** **Model No:** PE9212	 PRICE 1 Call - - - **HN Female to GR874 Sexless** **Model No:** PE9387
7	***LC In-Series*** →	 PRICE 1-9 $377.99 10-24 $359.09 25-49 $340.19 50+ $325.07 **LC Male to LC Male** **Model No:** PE9569	 PRICE 1-9 $505.00 10-24 $479.75 25-49 $454.50 50+ $434.30 **LC Male to LC Female Right Angle** **Model No:** PE9398	 PRICE 1-9 $313.99 10-24 $298.29 25-49 $282.59 50+ $270.03 **LC Female to LC Female** **Model No:** PE9419	***LC Between Series*** →

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-9 $381.99 10-24 $362.89 25-49 $343.79 50+ $328.51 **LC Male to HN Female** **Model No:** PE9181	 PRICE 1-9 $351.99 10-24 $334.39 25-49 $316.79 50+ $302.71 **LC Female to HN Male** **Model No:** PE9413	**MCX In-Series**	 PRICE 1-24 $90.99 25-49 $86.44 50-99 $81.89 100+ $78.25 **MCX Plug to MCX Jack** VSWR 1.35:1 to 6 GHz **Model No:** PE9479	 PRICE 1-24 $27.99 25-49 $26.59 50-99 $25.19 100+ $24.07 **MCX Jack to MCX Jack** **Model No:** PE9524
2	 PRICE 1-24 $36.19 25-49 $34.38 50-99 $32.57 100+ $31.12 **MCX Jack to MCX Jack Bulkhead** VSWR 1.35:1 to 3 GHz **Model No:** PE9474	**MCX Between Series**	 PRICE 1-24 $123.99 25-49 $117.79 50-99 $111.59 100+ $106.63 **MCX Plug to BNC Male** **Model No:** PE9469	 PRICE 1-24 $103.99 25-49 $98.79 50-99 $93.59 100+ $89.43 **MCX Plug to BNC Female** **Model No:** PE9467	 PRICE 1-24 $96.99 25-49 $92.14 50-99 $87.29 100+ $83.41 **MCX Jack to BNC Male** **Model No:** PE9468
3	 PRICE 1-24 $123.99 25-49 $117.79 50-99 $111.59 100+ $106.63 **MCX Jack to BNC Female** **Model No:** PE9466	 PRICE 1-24 $125.99 25-49 $119.69 50-99 $113.39 100+ $108.35 **MCX Jack to BNC Female Bulkhead-Mounting Hole B04** **Model No:** PE9520	**MHV In-Series**	 PRICE 1-24 $56.99 25-49 $54.14 50-99 $51.29 100+ $49.01 **MHV Male to BNC Female** VSWR 1.3:1 to 300 MHz **Model No:** PE9297	 PRICE 1-24 $75.99 25-49 $72.19 50-99 $68.39 100+ $65.35 **MHV Male to MHV Female Right Angle** Max. Freq. 50 MHz **Model No:** PE9266
4	 PRICE 1-24 $89.99 25-49 $85.49 50-99 $80.99 100+ $77.39 **MHV Female to MHV Male Tee** Max. Freq. 50 MHz **Model No:** PE9211	 PRICE 1-24 $49.19 25-49 $46.73 50-99 $44.27 100+ $42.30 **MHV Female to MHV Female** VSWR 1.3:1 to 300 MHz **Model No:** PE9267	 PRICE 1-24 $82.99 25-49 $78.84 50-99 $74.69 100+ $71.37 **MHV Female to MHV Female Bulkhead** **Model No:** PE9268	**MHV Between Series**	 PRICE 1-24 $129.99 25-49 $123.49 50-99 $116.99 100+ $111.79 **MHV Male to SHV Plug** **Model No:** PE9340
5	 PRICE 1-9 $167.99 10-24 $159.59 25-49 $151.19 50+ $144.47 **MHV Male to SHV Jack** **Model No:** PE9335	 PRICE 1-9 $145.99 10-24 $138.69 25-49 $131.39 50+ $125.55 **MHV Female to SHV Plug** **Model No:** PE9265	 PRICE 1-24 $85.99 25-49 $81.69 50-99 $77.39 100+ $73.95 **MHV Female to SHV Jack** **Model No:** PE9339	**Mini SMP In-Series**	 PRICE 1-24 $63.99 25-49 $60.79 50-99 $57.59 100+ $55.03 **Mini SMP Female to Mini SMP Female** Max. Freq. 65 GHz **Model No:** PE9780
6	 PRICE 1-24 $36.59 25-49 $34.76 50-99 $32.93 100+ $31.47 **Mini SMP Female to Mini SMP Female** VSWR 1.2:1 to 26.5 GHz **Model No:** PE91069	**Mini UHF In-Series**	 PRICE 1-24 $21.99 25-49 $20.89 50-99 $19.79 100+ $18.91 **Mini UHF Male to Mini UHF Female Right Angle** **Model No:** PE9347	 PRICE 1-24 $13.19 25-49 $12.53 50-99 $11.87 100+ $11.34 **Mini UHF Female to Mini UHF Male Tee** **Model No:** PE9065	 PRICE 1-24 $24.59 25-49 $23.36 50-99 $22.13 100+ $21.15 **Mini UHF Female to Mini UHF Female** **Model No:** PE9343
7	 PRICE 1-24 $22.59 25-49 $21.46 50-99 $20.33 100+ $19.43 **Mini UHF Female to Mini UHF Female Tee** **Model No:** PE9066	**Mini UHF Between Series**	 PRICE 1-24 $23.39 25-49 $22.22 50-99 $21.05 100+ $20.12 **Mini UHF Male to BNC Female** **Model No:** PE9342	 PRICE 1-24 $22.59 25-49 $21.46 50-99 $20.33 100+ $19.43 **Mini UHF Male to FME Plug** **Model No:** PE9705	 PRICE 1-24 $21.59 25-49 $20.51 50-99 $19.43 100+ $18.57 **Mini UHF Male to FME Plug Right Angle** **Model No:** PE9706

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $18.79 25-49 $17.85 50-99 $16.91 100+ $16.16 **Mini UHF Male to FME Jack** Model No: PE9709	 PRICE 1-24 $25.39 25-49 $24.12 50-99 $22.85 100+ $21.84 **Mini UHF Female to BNC Male** Model No: PE9341	 PRICE 1-24 $19.99 25-49 $18.99 50-99 $17.99 100+ $17.19 **Mini UHF Female to FME Jack** Model No: PE9710	***MMCX In-Series*** →	 PRICE 1-24 $117.99 25-49 $112.09 50-99 $106.19 100+ $101.47 **MMCX Plug to MMCX Jack** Model No: PE9480
2	 PRICE 1-24 $92.99 25-49 $88.34 50-99 $83.69 100+ $79.97 **MMCX Jack to MMCX Jack** Model No: PE9523	 PRICE 1-24 $83.99 25-49 $79.79 50-99 $75.59 100+ $72.23 **MMCX Jack to MMCX Jack Bulkhead-Mounting Hole B01** Model No: PE9522	***MMCX Between Series*** →	 PRICE 1-9 $141.99 10-24 $134.89 25-49 $127.79 50+ $122.11 **MMCX Plug to BNC Male** Model No: PE9517	 PRICE 1-24 $123.99 25-49 $117.79 50-99 $111.59 100+ $106.63 **MMCX Plug to MCX Plug** Model No: PE9527
3	 PRICE 1-24 $145.99 25-49 $138.69 50-99 $131.39 100+ $125.55 **MMCX Plug to MCX Jack** Model No: PE9525	 PRICE 1-24 $113.99 25-49 $108.29 50-99 $102.59 100+ $98.03 **MMCX Jack to BNC Male** Model No: PE9518	 PRICE 1-24 $121.99 25-49 $115.89 50-99 $109.79 100+ $104.91 **MMCX Jack to BNC Female** Model No: PE9516	 PRICE 1-24 $145.99 25-49 $138.69 50-99 $131.39 100+ $125.55 **MMCX Jack to MCX Plug** Model No: PE9528	 PRICE 1-24 $133.99 25-49 $127.29 50-99 $120.59 100+ $115.23 **MMCX Jack to MCX Jack** Model No: PE9526
4	***MMBX In-Series*** →	 PRICE 1-24 $13.39 25-49 $12.72 50-99 $12.05 100+ $11.52 **Slide-On MMBX Plug to Snap-On MMBX Plug** VSWR 1.08:1 to 12.4 GHz Model No: PE91370	 PRICE 1-24 $17.19 25-49 $16.33 50-99 $15.47 100+ $14.78 **Slide-On MMBX Plug to Slide-On MMBX Plug** VSWR 1.15:1 to 12.4 GHz Model No: PE91371	 PRICE 1-24 $21.79 25-49 $20.70 50-99 $19.61 100+ $18.74 **Snap-On MMBX Plug to Slide-On MMBX Plug** VSWR 1.25:1 to 12.4 GHz Model No: PE91372	 PRICE 1-24 $15.79 25-49 $15.00 50-99 $14.21 100+ $13.58 **Slide-On MMBX Plug to Snap-On MMBX Plug** VSWR 1.08:1 to 12.4 GHz Model No: PE91373
5	***N In-Series*** →	 PRICE 1-24 $73.99 25-49 $70.29 50-99 $66.59 100+ $63.63 **N Male to N Male** VSWR 1.2:1 to 6 GHz Model No: PE91198	 PRICE 1-24 $26.59 25-49 $25.26 50-99 $23.93 100+ $22.87 **N Male to N Male** VSWR 1.3:1 to 6 GHz Model No: PE9007	 PRICE 1-24 $123.99 25-49 $117.79 50-99 $111.59 Low PIM 100+ $106.63 **N Male to N Male** Max. Freq. 12.4 GHz Model No: PE91034	 PRICE 1-24 $105.99 25-49 $100.69 50-99 $95.39 PRECISION 100+ $91.15 **N Male to N Male** VSWR 1.15:1 to 18 GHz Model No: PE91532
6	 PRICE 1-24 $57.99 25-49 $55.09 50-99 $52.19 100+ $49.87 **N Male to N Male Right Angle** VSWR 1.5:1 to 11 GHz Model No: PE9198	 PRICE 1-24 $121.99 25-49 $115.89 50-99 $109.79 100+ $104.91 **N Male to N Male Tee** Model No: PE9390	 PRICE 1-24 $73.99 25-49 $70.29 50-99 $66.59 100+ $63.63 **N Male to N Female** VSWR 1.2:1 to 6 GHz Model No: PE91199	 PRICE 1-24 $58.99 25-49 $56.04 50-99 $53.09 100+ $50.73 **N Male to N Female** VSWR 1.3:1 to 6 GHz Model No: PE91236	 PRICE 1-24 $123.99 25-49 $117.79 50-99 $111.59 Low PIM 100+ $106.63 **N Male to N Female** Max. Freq. 12.4 GHz Model No: PE91040
7	 PRICE 1-24 $45.19 25-49 $42.93 50-99 $40.67 100+ $38.86 **Push-On N Male to N Female** VSWR 1.22:1 to 18 GHz Model No: PE91114	 PRICE 1-9 $105.99 10-24 $100.69 25-49 $95.39 PRECISION 50+ $91.15 **N Male to N Female** VSWR 1.15:1 to 18 GHz Model No: PE91531	 PRICE 1-24 $38.59 25-49 $36.66 50-99 $34.73 100+ $33.19 **N Male to N Female** VSWR 1.3:1 to 11 GHz Model No: PE9311	 PRICE 1-24 $70.99 25-49 $67.44 50-99 $63.89 100+ $61.05 **N Male to 75 Ohm N Female** Model No: PE9349	 PRICE 1-9 $225.99 10-24 $214.69 25-49 $203.39 50+ $194.35 **QD N Male to N Female** Model No: PE9547

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRECISION PRICE 1-9 $365.99, 10-24 $351.35, 25-49 $340.37, 50+ $333.05 **N Male to N Female** **Radius Right Angle** VSWR 1.25:1 to 18 GHz **Model No:** PE91350	 PRICE 1-24 $28.79, 25-49 $27.35, 50-99 $25.91, 100+ $24.76 **N Male to N Female** **Right Angle** VSWR 1.3:1 to 11 GHz **Model No:** PE9086	 PRICE 1-24 $123.99, 25-49 $117.79, 50-99 $111.59, 100+ $106.63 **N Male to N Female** **Tee** **Model No:** PE9481	 PRICE 1-24 $51.99, 25-49 $49.39, 50-99 $46.79, 100+ $44.71 **N Male to N Female** **Bulkhead** VSWR 1.3:1 to 11 GHz **Model No:** PE9595	 PRICE 1-24 $60.99, 25-49 $57.94, 50-99 $54.89, 100+ $52.45 **N Female to 75 Ohm N Male** Max. Freq. 500 MHz **Model No:** PE9350
2	 PRICE 1-24 $67.99, 25-49 $64.59, 50-99 $61.19, 100+ $58.47 **N Female to N Male** **Tee** Max. Freq. 11 GHz **Model No:** PE9102	 PRICE 1-24 $85.99, 25-49 $81.69, 50-99 $77.39, 100+ $73.95 **N Female to N Female** VSWR 1.2:1 to 6 GHz **Model No:** PE91200	 PRICE 1-24 $48.19, 25-49 $45.78, 50-99 $43.37, 100+ $41.44 **N Female to N Female** VSWR 1.3:1 to 6 GHz **Model No:** PE91237	 PRICE 1-24 $23.59, 25-49 $22.41, 50-99 $21.23, 100+ $20.29 **N Female to N Female** VSWR 1.3:1 to 11 GHz **Model No:** PE9006	 Low PIM PRICE 1-24 $90.99, 25-49 $86.44, 50-99 $81.89, 100+ $78.25 **N Female to N Female** VSWR 1.2:1 to 6 GHz **Model No:** PE91140
3	 PRICE 1-24 $61.99, 25-49 $58.89, 50-99 $55.79, 100+ $53.31 **N Female to N Female** VSWR 1.2:1 to 18 GHz **Model No:** PE91141	 PRECISION PRICE 1-9 $131.99, 10-24 $125.39, 25-49 $118.79, 50+ $113.51 **N Female to N Female** VSWR 1.15:1 to 18 GHz **Model No:** PE91530	 PRICE 1-24 $67.99, 25-49 $64.59, 50-99 $61.19, 100+ $58.47 **N Female to N Female** **Right Angle** Max. Freq. 11 GHz **Model No:** PE9359	 PRICE 1-24 $52.99, 25-49 $50.34, 50-99 $47.69, 100+ $45.57 **N Female to N Female** **Tee** VSWR 2:1 to 100 MHz **Model No:** PE9101	 PRICE 1-24 $125.99, 25-49 $119.69, 50-99 $113.39, 100+ $108.35 **N Female to N Female** **Cross** **Model No:** PE9548
4	 PRICE 1-24 $36.99, 25-49 $35.14, 50-99 $33.29, 100+ $31.81 **N Female to N Female** **Bulkhead** VSWR 1.4:1 to 3 GHz **Model No:** PE9128	 PRICE 1-24 $88.99, 25-49 $84.54, 50-99 $80.09, 100+ $76.53 **N Female to N Female** **Bulkhead** Max. Freq. 11 GHz **Model No:** PE9383	 PRICE 1-24 $101.99, 25-49 $96.89, 50-99 $91.79, 100+ $87.71 **N Female to N Female** **Right Angle Bulkhead-** **Mounting Hole G01** Max. Freq. 6 GHz **Model No:** PE9541	 PRICE 1-24 $40.99, 25-49 $38.94, 50-99 $36.89, 100+ $35.25 **N Female to N Female** **4 Hole Flange-Mounting Hole** **A05** VSWR 1.5:1 to 11 GHz **Model No:** PE9173	 PRECISION PRICE 1-9 $173.99, 10-24 $165.29, 25-49 $156.59, 50+ $149.63 **N Female to N Female** **4 Hole Flange-Mounting Hole** **A05** VSWR 1.15:1 to 18 GHz **Model No:** PE9429
5	 PRICE 1-24 $90.99, 25-49 $86.44, 50-99 $81.89, 100+ $78.25 **N Female to N Female** **Bulkhead** VSWR 1.2:1 to 6 GHz **Model No:** PE91201	 PRICE 1-24 $46.19, 25-49 $43.88, 50-99 $41.57, 100+ $39.72 **N Female to N Female** **Bulkhead** VSWR 1.3:1 to 6 GHz **Model No:** PE91238	 Low PIM PRICE 1-24 $81.99, 25-49 $77.89, 50-99 $73.79, 100+ $70.51 **N Female to N Female** **Bulkhead** VSWR 1.2:1 to 6 GHz **Model No:** PE91179	 PRECISION PRICE 1-9 $211.99, 10-24 $201.39, 25-49 $190.79, 50+ $182.31 **N Female to N Female** **Bulkhead** VSWR 1.15:1 to 18 GHz **Model No:** PE9500	 PRICE 1-24 $62.99, 25-49 $59.84, 50-99 $56.69, 100+ $54.17 **N Female to N Female** **Bulkhead** VSWR 1.5:1 to 11 GHz **Model No:** PE9382
6	***N*** ***Between Series*** →	 PRECISION PRICE 1-9 $443.99, 10-24 $421.79, 25-49 $399.59, 50+ $381.83 **N Male to 7mm Sexless** VSWR 1.12:1 to 18 GHz **Model No:** PE9217	 Low PIM PRICE 1-24 $93.99, 25-49 $89.29, 50-99 $84.59, 100+ $80.83 **N Male to 4.3-10 Female** VSWR 1.08:1 to 6 GHz **Model No:** PE91388	 PRICE 1-9 $241.99, 10-24 $229.89, 25-49 $217.79, 50+ $208.11 **N Male to 7/16 DIN Male** **Model No:** PE9535	 Low PIM PRICE 1-24 $133.99, 25-49 $127.29, 50-99 $120.59, 100+ $115.23 **N Male to 7/16 DIN Female** Max. Freq. 8 GHz **Model No:** PE91032
7	 PRICE 1-24 $111.99, 25-49 $106.39, 50-99 $100.79, 100+ $96.31 **N Male to 7/16 DIN Female** VSWR 1.15:1 to 6 GHz **Model No:** PE91134	 PRICE 1-24 $57.99, 25-49 $55.09, 50-99 $52.19, 100+ $49.87 **N Male to BNC Male** VSWR 1.3:1 to 4 GHz **Model No:** PE9127	 PRECISION PRICE 1-9 $223.99, 10-24 $212.79, 25-49 $201.59, 50+ $192.63 **N Male to BNC Male** VSWR 1.2:1 to 8 GHz **Model No:** PE9489	 PRICE 1-24 $129.99, 25-49 $123.49, 50-99 $116.99, 100+ $111.79 **N Male to BNC Male** **Right Angle** **Model No:** PE9565	 PRICE 1-24 $28.19, 25-49 $26.78, 50-99 $25.37, 100+ $24.24 **N Male to BNC Female** VSWR 1.3:1 to 2 GHz **Model No:** PE9002

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRECISION 1-9 $179.99 10-24 $170.99 25-49 $161.99 50+ $154.79 **N Male to BNC Female** VSWR 1.2:1 to 8 GHz **Model No:** PE9491	 1-24 $105.99 25-49 $100.69 50-99 $95.39 100+ $91.15 **N Male to BNC Female Right Angle** VSWR 1.2:1 to 4 GHz **Model No:** PE9278	 1-24 $79.99 25-49 $75.99 50-99 $71.99 100+ $68.79 **N Male to BNC Female 4 Hole Flange** Max. Freq. 4 GHz **Model No:** PE9388	 1-24 $125.99 25-49 $119.69 50-99 $113.39 100+ $108.35 **N Male to C Male** **Model No:** PE9538	 1-24 $72.99 25-49 $69.34 50-99 $65.69 100+ $62.77 **N Male to C Female** Max. Freq. 11 GHz **Model No:** PE91446
2	 1-24 $131.99 25-49 $125.39 50-99 $118.79 100+ $113.51 **N Male to C Female Right Angle** Max. Freq. 4 GHz **Model No:** PE9239	 1-24 $41.99 25-49 $39.89 50-99 $37.79 100+ $36.11 **N Male to 75 Ohm F Female** VSWR 1.3:1 to 250 MHz **Model No:** PE9155	 1-24 $31.19 25-49 $29.63 50-99 $28.07 100+ $26.82 **N Male to FME Plug** **Model No:** PE9704	 1-9 $229.99 10-24 $218.49 25-49 $206.99 50+ $197.79 **N Male to GR874 Sexless** **Model No:** PE9257	 1-24 $103.99 25-49 $98.79 50-99 $93.59 100+ $89.43 **N Male to HN Male** **Model No:** PE9554
3	 1-24 $70.99 25-49 $67.44 50-99 $63.89 100+ $61.05 **N Male to HN Female** VSWR 1.3:1 to 4 GHz **Model No:** PE9125	 1-9 $241.99 10-24 $229.89 25-49 $217.79 50+ $208.11 **N Male to LC Female** **Model No:** PE9299	 1-24 $111.99 25-49 $107.51 50-99 $104.15 100+ $101.91 **N Male to MCX Plug** **Model No:** PE9465	 1-9 $159.99 10-24 $151.99 25-49 $143.99 50+ $137.59 **N Male to MCX Jack** Max. Freq. 6 GHz **Model No:** PE9464	 1-24 $31.59 25-49 $30.01 50-99 $28.43 100+ $27.17 **N Male to Mini UHF Female** Max. Freq. 2.5 GHz **Model No:** PE9064
4	 1-9 $159.99 10-24 $151.99 25-49 $143.99 50+ $137.59 **N Male to SC Male** VSWR 1.25:1 to 11 GHz **Model No:** PE9570	 1-9 $135.99 10-24 $129.19 25-49 $122.39 50+ $116.95 **N Male to SC Female** VSWR 1.25:1 to 11 GHz **Model No:** PE9196	 Low PIM 1-24 $60.99 25-49 $57.94 50-99 $54.89 100+ $52.45 **N Male to SMA Female** VSWR 1.2:1 to 6 GHz **Model No:** PE91177	 PRECISION 1-24 $65.99 25-49 $62.69 50-99 $59.39 100+ $56.75 **N Male to SMA Female** VSWR 1.25:1 to 18 GHz **Model No:** PE91339	 1-24 $123.99 25-49 $117.79 50-99 $111.59 100+ $106.63 **N Male to SMB Plug** **Model No:** PE9314
5	 1-24 $82.99 25-49 $78.84 50-99 $74.69 100+ $71.37 **N Male to SMB Jack** **Model No:** PE9313	 1-24 $121.99 25-49 $115.89 50-99 $109.79 100+ $104.91 **N Male to SMC Plug** **Model No:** PE9318	 1-24 $107.99 25-49 $102.59 50-99 $97.19 100+ $92.87 **N Male to SMC Jack** **Model No:** PE9317	 1-24 $31.99 25-49 $30.39 50-99 $28.79 100+ $27.51 **N Male to TNC Male** VSWR 1.5:1 to 11 GHz **Model No:** PE9130	 PRECISION 1-9 $195.99 10-24 $186.19 25-49 $176.39 50+ $168.55 **N Male to TNC Male** VSWR 1.15:1 to 18 GHz **Model No:** PE9446
6	 1-24 $30.79 25-49 $29.25 50-99 $27.71 100+ $26.48 **N Male to TNC Female** VSWR 1.5:1 to 1,000 MHz **Model No:** PE9090	 1-24 $105.99 25-49 $100.69 50-99 $95.39 100+ $91.15 **N Male to TNC Female Right Angle** VSWR 1.33:1 to 6 GHz **Model No:** PE9550	 1-9 $135.99 10-24 $129.19 25-49 $122.39 50+ $116.95 **N Male to TNC Female** VSWR 1.15:1 to 18 GHz **Model No:** PE91537	 1-24 $45.19 25-49 $42.93 50-99 $40.67 100+ $38.86 **N Male to UHF Male** **Model No:** PE9113	 1-24 $43.19 25-49 $41.03 50-99 $38.87 100+ $37.14 **N Male to UHF Female** VSWR 1.3:1 to 300 MHz **Model No:** PE9111
7	 Low PIM 1-24 $56.99 25-49 $54.14 50-99 $51.29 100+ $49.01 **N Male to 2.2-5 Male** VSWR 1.25:1 to 8 GHz **Model No:** PE9796	 Low PIM 1-24 $53.99 25-49 $51.29 50-99 $48.59 100+ $46.43 **N Male to 2.2-5 Female** VSWR 1.25:1 to 8 GHz **Model No:** PE9797	 PRECISION 1-9 $437.99 10-24 $420.47 25-49 $407.33 50+ $398.57 **N Female to 7mm Sexless** VSWR 1.15:1 to 18 GHz **Model No:** PE9216	 Low PIM 1-24 $125.99 25-49 $119.69 50-99 $113.39 100+ $108.35 **N Female to 7/16 DIN Male** Max. Freq. 8 GHz **Model No:** PE91031	 Low PIM 1-9 $177.99 10-24 $169.09 25-49 $160.19 50+ $153.07 **N Female to 7/16 DIN Female** Max. Freq. 8 GHz **Model No:** PE9180

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $25.99 25-49 $24.69 50-99 $23.39 100+ $22.35 **N Female to BNC Male** VSWR 1.3:1 to 4 GHz **Model No: PE9005**	 PRECISION PRICE 1-9 $173.99 10-24 $165.29 25-49 $156.59 50+ $149.63 **N Female to BNC Male** VSWR 1.2:1 to 8 GHz **Model No: PE9490**	 PRICE 1-24 $78.99 25-49 $75.04 50-99 $71.09 100+ $67.93 **N Female to BNC Male** **Right Angle** Max. Freq. 4 GHz **Model No: PE9566**	 PRICE 1-24 $103.99 25-49 $98.79 50-99 $93.59 100+ $89.43 **N Female to BNC Male** **4 Hole Flange-Mounting Hole A05** **Model No: PE9123**	 PRICE 1-24 $27.59 25-49 $26.21 50-99 $24.83 100+ $23.73 **N Female to BNC Female** VSWR 1.5:1 to 3 GHz **Model No: PE9206**
2	 PRECISION PRICE 1-9 $207.99 10-24 $197.59 25-49 $187.19 50+ $178.87 **N Female to BNC Female** VSWR 1.2:1 to 8 GHz **Model No: PE9492**	 PRICE 1-24 $82.99 25-49 $78.84 50-99 $74.69 100+ $71.37 **N Female to BNC Female** **Bulkhead-Mounting Hole G01** **Model No: PE9261**	 PRICE 1-24 $73.99 25-49 $70.29 50-99 $66.59 100+ $63.63 **N Female to BNC Female** **4 Hole Flange-Mounting Hole A05** VSWR 1.2:1 to 6 GHz **Model No: PE9238**	 PRICE 1-24 $81.99 25-49 $77.89 50-99 $73.79 100+ $70.51 **N Female to BNC Female** **Bulkhead-Mounting Hole G01** Max. Freq. 4 GHz **Model No: PE9540**	 PRICE 1-24 $78.99 25-49 $75.04 50-99 $71.09 100+ $67.93 **N Female to C Male** VSWR 1.25:1 to 11 GHz **Model No: PE9295**
3	 PRICE 1-24 $115.99 25-49 $110.19 50-99 $104.39 100+ $99.75 **N Female to C Female** **Model No: PE9539**	 PRICE 1-24 $52.99 25-49 $50.34 50-99 $47.69 100+ $45.57 **N Female to 75 Ohm F Male** VSWR 1.3:1 to 250 MHz **Model No: PE9389**	 PRICE 1-9 $221.99 10-24 $210.89 25-49 $199.79 50+ $190.91 **N Female to GR874 Sexless** **Model No: PE9258**	 PRICE 1-24 $68.99 25-49 $65.54 50-99 $62.09 100+ $59.33 **N Female to HN Male** VSWR 1.3:1 to 3 GHz **Model No: PE9194**	 PRICE 1-24 $96.99 25-49 $92.14 50-99 $87.29 100+ $83.41 **N Female to HN Female** **Model No: PE9360**
4	 PRICE 1-24 $141.99 25-49 $134.89 50-99 $127.79 100+ $122.11 **N Female to HN Female** **4 Hole Flange-Mounting Hole A08** **Model No: PE9553**	 PRICE 1-9 $363.99 10-24 $345.79 25-49 $327.59 50+ $313.03 **N Female to LC Male** Max. Freq. 1,000 MHz **Model No: PE9237**	 PRICE 1-9 $337.99 10-24 $321.09 25-49 $304.19 50+ $290.67 **N Female to LC Female** **Model No: PE9298**	 PRICE 1-24 $127.99 25-49 $122.87 50-99 $119.03 100+ $116.47 **N Female to MCX Plug** Max. Freq. 6 GHz **Model No: PE9463**	 PRICE 1-9 $159.99 10-24 $151.99 25-49 $143.99 50+ $137.59 **N Female to MCX Jack** Max. Freq. 6 GHz **Model No: PE9462**
5	 PRICE 1-24 $33.39 25-49 $31.72 50-99 $30.05 100+ $28.72 **N Female to Mini UHF Male** VSWR 1.5:1 to 2.5 GHz **Model No: PE9183**	 PRICE 1-9 $137.99 10-24 $131.09 25-49 $124.19 50+ $118.67 **N Female to SC Male** VSWR 1.25:1 to 11 GHz **Model No: PE9277**	 PRICE 1-9 $137.99 10-24 $131.09 25-49 $124.19 50+ $118.67 **N Female to SC Female** VSWR 1.25:1 to 11 GHz **Model No: PE9292**	 Low PIM PRICE 1-24 $61.99 25-49 $58.89 50-99 $55.79 100+ $53.31 **N Female to SMA Male** VSWR 1.2:1 to 6 GHz **Model No: PE91178**	 PRICE 1-24 $90.99 25-49 $86.44 50-99 $81.89 100+ $78.25 **N Female to SMB Plug** **Model No: PE9316**
6	 PRICE 1-24 $90.99 25-49 $86.44 50-99 $81.89 100+ $78.25 **N Female to SMB Jack** **Model No: PE9315**	 PRICE 1-24 $129.99 25-49 $123.49 50-99 $116.99 100+ $111.79 **N Female to SMC Plug** **Model No: PE9320**	 PRICE 1-24 $105.99 25-49 $100.69 50-99 $95.39 100+ $91.15 **N Female to SMC Jack** **Model No: PE9319**	 PRICE 1-24 $24.79 25-49 $23.55 50-99 $22.31 100+ $21.32 **N Female to TNC Male** VSWR 1.3:1 to 6 GHz **Model No: PE9089**	 PRECISION PRICE 1-24 $157.99 25-49 $146.93 50-99 $135.87 100+ $126.39 **N Female to TNC Male** VSWR 1.2:1 to 18 GHz **Model No: PE91506**
7	 PRICE 1-24 $81.99 25-49 $77.89 50-99 $73.79 100+ $70.51 **N Female to TNC Male** **Right Angle** VSWR 1.5:1 to 6 GHz **Model No: PE9263**	 PRICE 1-24 $36.79 25-49 $34.95 50-99 $33.11 100+ $31.64 **N Female to TNC Female** VSWR 1.5:1 to 3 GHz **Model No: PE9131**	 PRECISION PRICE 1-9 $237.99 10-24 $226.09 25-49 $214.19 50+ $204.67 **N Female to TNC Female** VSWR 1.15:1 to 18 GHz **Model No: PE9449**	 PRICE 1-24 $111.99 25-49 $106.39 50-99 $100.79 100+ $96.31 **N Female to TNC Female** **4 Hole Flange-Mounting Hole A05** **Model No: PE9552**	 PRICE 1-24 $59.99 25-49 $56.99 50-99 $53.99 100+ $51.59 **N Female to TNC Female** **Bulkhead** VSWR 1.35:1 to 10 GHz **Model No: PE9482**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRECISION PRICE 1-9 $185.99; 10-24 $176.69; 25-49 $167.39; 50+ $159.95 **N Female to TNC Female 4 Hole Flange-Mounting Hole A05** VSWR 1.15:1 to 18 GHz **Model No:** PE9450	 PRICE 1-24 $39.99; 25-49 $37.99; 50-99 $35.99; 100+ $34.39 **N Female to UHF Male** VSWR 1.3:1 to 300 MHz **Model No:** PE9112	 PRICE 1-24 $47.59; 25-49 $45.21; 50-99 $42.83; 100+ $40.93 **N Female to UHF Female** Max. Freq. 1,000 MHz **Model No:** PE9385	 Low PIM PRICE 1-24 $56.99; 25-49 $54.14; 50-99 $51.29; 100+ $49.01 **N Female to 2.2-5 Male** VSWR 1.25:1 to 8 GHz **Model No:** PE9794	 Low PIM PRICE 1-24 $53.99; 25-49 $51.29; 50-99 $48.59; 100+ $46.43 **N Female to 2.2-5 Female** VSWR 1.25:1 to 8 GHz **Model No:** PE9795
2	***Reverse Polarity N In-Series*** →	 PRICE 1-24 $55.99; 25-49 $53.19; 50-99 $50.39; 100+ $48.15 **N Male to Rev. Pol. N Female** Max. Freq. 11 GHz **Model No:** PE9771	 PRICE 1-24 $63.99; 25-49 $60.79; 50-99 $57.59; 100+ $55.03 **N Female to Rev. Pol. N Male** Max. Freq. 11 GHz **Model No:** PE9770	 PRICE 1-24 $58.99; 25-49 $56.04; 50-99 $53.09; 100+ $50.73 **Rev. Pol. N Female to Rev. Pol. N Female** VSWR 1.3:1 to 11 GHz **Model No:** PE9773	***Reverse Polarity N Between Series*** →
3	 PRICE 1-24 $60.99; 25-49 $57.94; 50-99 $54.89; 100+ $52.45 **N Male to Rev. Pol. TNC Female** VSWR 1.3:1 to 6 GHz **Model No:** PE9730	 PRICE 1-24 $59.99; 25-49 $56.99; 50-99 $53.99; 100+ $51.59 **N Female to Rev. Pol. TNC Male** **Model No:** PE9731	***QMA In-Series*** →	 PRICE 1-24 $70.99; 25-49 $67.44; 50-99 $63.89; 100+ $61.05 **Snap-On QMA Male to Snap-On QMA Male** VSWR 1.08:1 to 6 GHz **Model No:** PE91341	 PRICE 1-24 $42.59; 25-49 $40.46; 50-99 $38.33; 100+ $36.63 **Snap-On QMA Male to Snap-On QMA Female** VSWR 1.12:1 to 6 GHz **Model No:** PE91342
4	 PRICE 1-9 $203.99; 10-24 $193.79; 25-49 $183.59; 50+ $175.43 **Snap-On QMA Female to Snap-On QMA Female** VSWR 1.08:1 to 6 GHz **Model No:** PE91343	***QMA Between Series*** →	 PRICE 1-9 $209.99; 10-24 $199.49; 25-49 $188.99; 50+ $180.59 **Snap-On QMA Male to Snap-On SMA Male** VSWR 1.18:1 to 6 GHz **Model No:** PE91344	 PRICE 1-24 $75.99; 25-49 $72.19; 50-99 $68.39; 100+ $65.35 **Snap-On QMA Male to SMA Female** VSWR 1.18:1 to 6 GHz **Model No:** PE91345	 PRICE 1-24 $63.99; 25-49 $60.79; 50-99 $57.59; 100+ $55.03 **Snap-On QMA Female to SMA Male** VSWR 1.18:1 to 6 GHz **Model No:** PE91346
5	 PRICE 1-9 $129.99; 10-24 $123.49; 25-49 $116.99; 50+ $111.79 **Snap-On QMA Female to Snap-On SMA Female** VSWR 1.18:1 to 6 GHz **Model No:** PE91347	***SC In-Series*** →	 PRICE 1-9 $139.99; 10-24 $132.99; 25-49 $125.99; 50+ $120.39 **SC Male to SC Male** **Model No:** PE9403	 PRICE 1-9 $203.99; 10-24 $193.79; 25-49 $183.59; 50+ $175.43 **SC Male to SC Female Right Angle** **Model No:** PE9405	 PRICE 1 Call; - ; - ; - **SC Female to SC Male Tee** **Model No:** PE9225
6	 PRICE 1-9 $147.99; 10-24 $140.59; 25-49 $133.19; 50+ $127.27 **SC Female to SC Female** VSWR 1.25:1 to 11 GHz **Model No:** PE9404	 PRICE 1-9 $189.99; 10-24 $180.49; 25-49 $170.99; 50+ $163.39 **SC Female to SC Female Bulkhead** **Model No:** PE9573	***SC Between Series*** →	 PRICE 1-24 $70.99; 25-49 $67.44; 50-99 $63.89; 100+ $61.05 **SC Male to BNC Male** **Model No:** PE9568	 PRICE 1-24 $94.99; 25-49 $90.24; 50-99 $85.49; 100+ $81.69 **SC Female to BNC Female** **Model No:** PE9571
7	***SHV In-Series*** →	 PRICE 1-9 $159.99; 10-24 $151.99; 25-49 $143.99; 50+ $137.59 **SHV Plug to SHV Jack** **Model No:** PE9749	 PRICE 1-24 $103.99; 25-49 $98.79; 50-99 $93.59; 100+ $89.43 **SHV Plug to SHV Jack Right Angle** **Model No:** PE9338	 PRICE 1-24 $121.99; 25-49 $115.89; 50-99 $109.79; 100+ $104.91 **SHV Jack to SHV Plug Tee** VSWR 1.2:1 to 300 MHz **Model No:** PE9249	 PRICE 1-24 $54.99; 25-49 $52.24; 50-99 $49.49; 100+ $47.29 **SHV Jack to SHV Jack** VSWR 1.3:1 to 300 MHz **Model No:** PE9337

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $101.99 25-49 $96.89 50-99 $91.79 100+ $87.71 **SHV Jack to SHV Jack Bulkhead** Max. Freq. 300 MHz **Model No:** PE9336	***SMA In-Series*** 	 PRICE 1-24 $24.39 25-49 $23.17 50-99 $21.95 100+ $20.98 **SMA Male to SMA Male** VSWR 1.23:1 to 18 GHz **Model No:** PE91135	 PRECISION PRICE 1-24 $85.99 25-49 $81.69 50-99 $77.39 100+ $73.95 **SMA Male to SMA Male** VSWR 1.2:1 to 27 GHz **Model No:** PE9505	 PRICE 1-24 $94.99 25-49 $90.24 50-99 $85.49 100+ $81.69 **SMA Male to SMA Male Radius Right Angle** VSWR 1.35:1 to 26 GHz **Model No:** PE91496
2	 PRICE 1-24 $96.99 25-49 $92.14 50-99 $87.29 100+ $83.41 **SMA Male to SMA Male Radius Right Angle** VSWR 1.35:1 to 26 GHz **Model No:** PE91497	 PRICE 1-24 $64.99 25-49 $61.74 50-99 $58.49 100+ $55.89 **SMA Male to SMA Male Right Angle** VSWR 1.5:1 to 12.4 GHz **Model No:** PE9418	 PRICE 1-24 $99.99 25-49 $94.99 50-99 $89.99 100+ $85.99 **SMA Male to SMA Male Tee** **Model No:** PE9379	 PRECISION PRICE 1-24 $121.99 25-49 $115.89 50-99 $109.79 100+ $104.91 **SMA Male to SMA Male Miter Right Angle** VSWR 1.15:1 to 27 GHz **Model No:** PE91151	 PRICE 1-24 $109.99 25-49 $104.49 50-99 $98.99 100+ $94.59 **SMA Male to SMA Male Miter Right Angle** VSWR 1.35:1 to 27 GHz **Model No:** PE9642
3	 PRICE 1-9 $255.99 10-24 $245.75 25-49 $238.07 50+ $232.95 **SMA Male to SMA Male 4 Hole Flange-Mounting Hole A01** VSWR 1.2:1 to 18 GHz **Model No:** PE9669	 PRICE 1-24 $38.79 25-49 $36.85 50-99 $34.91 100+ $33.36 **SMA Male to SMA Male** VSWR 1.2:1 to 27 GHz **Model No:** PE91535	 PRICE 1-24 $32.79 25-49 $31.15 50-99 $29.51 100+ $28.20 **SMA Male to SMA Female** VSWR 1.25:1 to 18 GHz **Model No:** PE9103	 PRECISION PRICE 1 Call - - - **SMA Male to SMA Female** VSWR 1.2:1 to 27 GHz **Model No:** PE9506	 PRICE 1-24 $36.99 25-49 $35.14 50-99 $33.29 100+ $31.81 **QD SMA Male to SMA Female** **Model No:** PE9546
4	 PRECISION PRICE 1-24 $61.99 25-49 $58.89 50-99 $55.79 100+ $53.31 **SMA Male to SMA Female** VSWR 1.2:1 to 18 GHz **Model No:** PE9694	 PRECISION PRICE 1-9 $173.99 10-24 $165.29 25-49 $156.59 50+ $149.63 **QD SMA Male to SMA Female** VSWR 1.14:1 to 18 GHz **Model No:** PE9774	 PRICE 1-24 $68.99 25-49 $65.54 50-99 $62.09 100+ $59.33 **SMA Male to SMA Female Radius Right Angle** VSWR 1.2:1 to 18 GHz **Model No:** PE91492	 PRICE 1-24 $71.99 25-49 $68.39 50-99 $64.79 100+ $61.91 **SMA Male to SMA Female Radius Right Angle** VSWR 1.2:1 to 18 GHz **Model No:** PE91493	 PRICE 1-31 $103.99 32-31 NULL 32-31 NULL 32+ NULL **SMA Male to SMA Female Radius Right Angle** VSWR 1.25:1 to 18 GHz **Model No:** PE91155
5	 PRICE 1-24 $91.99 25-49 $87.39 50-99 $82.79 100+ $79.11 **SMA Male to SMA Female Radius Right Angle** VSWR 1.55:1 to 26.5 GHz **Model No:** PE91222	 PRICE 1-24 $37.39 25-49 $35.52 50-99 $33.65 100+ $32.16 **SMA Male to SMA Female Right Angle** VSWR 1.23:1 to 12.4 GHz **Model No:** PE9068	 PRECISION PRICE 1-24 $119.99 25-49 $113.99 50-99 $107.99 100+ $103.19 **SMA Male to SMA Female 45 Degree Right** VSWR 1.3:1 to 27 GHz **Model No:** PE91332	 PRICE 1-24 $98.99 25-49 $94.04 50-99 $89.09 100+ $85.13 **SMA Male to SMA Female Tee** VSWR 2.25:1 to 6 GHz **Model No:** PE9247	 PRICE 1-24 $64.99 25-49 $61.74 50-99 $58.49 100+ $55.89 **SMA Male to SMA Female Bulkhead** VSWR 1.3:1 to 18 GHz **Model No:** PE9621
6	 PRICE 1-24 $96.99 25-49 $90.20 50-99 $83.41 100+ $77.59 **SMA Male to SMA Female 4 Hole Flange** VSWR 1.2:1 to 18 GHz **Model No:** PE91453	 PRICE 1-24 $31.99 25-49 $30.39 50-99 $28.79 100+ $27.51 **Push-On SMA Male to SMA Female Bulkhead** VSWR 1.23:1 to 18 GHz **Model No:** PE91321	 PRECISION PRICE 1-24 $87.99 25-49 $83.59 50-99 $79.19 100+ $75.67 **SMA Male to SMA Female Miter Right Angle** VSWR 1.2:1 to 27 GHz **Model No:** PE91504	 PRICE 1-24 $58.99 25-49 $56.04 50-99 $53.09 100+ $50.73 **SMA Female to SMA Male Tee** Max. Freq. 6 GHz **Model No:** PE9182	 PRICE 1-24 $22.99 25-49 $21.84 50-99 $20.69 100+ $19.77 **SMA Female to SMA Female** VSWR 1.25:1 to 18 GHz **Model No:** PE9070
7	 PRICE 1-24 $40.19 25-49 $38.18 50-99 $36.17 100+ $34.56 **SMA Female to SMA Female** VSWR 1.23:1 to 18 GHz **Model No:** PE9380	 PRECISION PRICE 1-24 $53.99 25-49 $51.29 50-99 $48.59 100+ $46.43 **SMA Female to SMA Female** VSWR 1.15:1 to 18 GHz **Model No:** PE9695	 PRICE 1-24 $95.99 25-49 $91.19 50-99 $86.39 100+ $82.55 **SMA Female to SMA Female Radius Right Angle** VSWR 1.25:1 to 18 GHz **Model No:** PE91494	 PRICE 1-24 $97.99 25-49 $93.09 50-99 $88.19 100+ $84.27 **SMA Female to SMA Female Radius Right Angle** VSWR 1.25:1 to 18 GHz **Model No:** PE91495	 PRICE 1-24 $70.99 25-49 $67.44 50-99 $63.89 100+ $61.05 **SMA Female to SMA Female Right Angle** **Model No:** PE9485

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $79.99 25-49 $75.99 50-99 $71.99 100+ $68.79 **SMA Female to SMA Female Tee** Max. Freq. 6 GHz **Model No: PE9246**	 PRICE 1-24 $74.99 25-49 $71.24 50-99 $67.49 100+ $64.49 **SMA Female to SMA Female Bulkhead-Mounting Hole B02** VSWR 1.23:1 to 18 GHz **Model No: PE9014**	 PRICE 1-24 $23.79 25-49 $22.60 50-99 $21.41 100+ $20.46 **SMA Female to SMA Female Bulkhead** VSWR 1.25:1 to 18 GHz **Model No: PE91258**	 PRICE 1-9 $131.99 10-24 $125.39 25-49 $118.79 50+ $113.51 **SMA Female to SMA Female Bulkhead-Mounting Hole B02** VSWR 1.3:1 to 26.5 GHz **Model No: PE9508**	 PRECISION PRICE 1-24 $54.99 25-49 $52.24 50-99 $49.49 100+ $47.29 **SMA Female to SMA Female Bulkhead-Mounting Hole B02** VSWR 1.15:1 to 18 GHz **Model No: PE9620**
2	 PRICE 1-9 $53.99 10-24 $51.29 25-49 $48.59 50+ $46.43 **SMA Female to SMA Female Bulkhead** VSWR 1.35:1 to 18 GHz **Model No: PE91393**	 PRICE 1-24 $60.99 25-49 $57.94 50-99 $54.89 100+ $52.45 **SMA Female to SMA Female Bulkhead** VSWR 1.4:1 to 18 GHz **Model No: PE9184**	 PRICE 1-24 $42.99 25-49 $40.84 50-99 $38.69 100+ $36.97 **SMA Female to SMA Female Bulkhead** VSWR 1.25:1 to 12.4 GHz **Model No: PE9067**	 PRICE 1-24 $77.99 25-49 $74.09 50-99 $70.19 100+ $67.07 **SMA Female to SMA Female 4 Hole Flange-Mounting Hole A01** VSWR 1.25:1 to 18 GHz **Model No: PE9312**	 PRICE 1-24 $117.99 25-49 $112.09 50-99 $106.19 100+ $101.47 **SMA Female to SMA Female 4 Hole Flange-Mounting Hole A01** VSWR 1.25:1 to 18 GHz **Model No: PE9670**
3	 PRICE 1-24 $34.19 25-49 $32.48 50-99 $30.77 100+ $29.40 **SMA Female to SMA Female Bulkhead** VSWR 1.23:1 to 18 GHz **Model No: PE9184NH**	 PRICE 1-24 $24.79 25-49 $23.55 50-99 $22.31 100+ $21.32 **SMA Female to SMA Female 2 Hole Flange** VSWR 1.25:1 to 18 GHz **Model No: PE91290**	 PRECISION PRICE 1-24 $37.59 25-49 $35.71 50-99 $33.83 100+ $32.33 **SMA Female to SMA Female** VSWR 1.2:1 to 27 GHz **Model No: PE91549**	 PRECISION PRICE 1-24 $101.99 25-49 $96.89 50-99 $91.79 100+ $87.71 **SMA Female to SMA Female Miter Right Angle** VSWR 1.2:1 to 27 GHz **Model No: PE91176**	***SMA Between Series*** 
4	 PRICE 1-24 $135.99 25-49 $129.19 50-99 $122.39 100+ $116.95 **SMA Male to 1.0/2.3 Plug** **Model No: PE9692**	 PRICE 1-24 $113.99 25-49 $108.29 50-99 $102.59 100+ $98.03 **SMA Male to 1.0/2.3 Jack** **Model No: PE9690**	 PRICE 1-9 $291.99 10-24 $277.39 25-49 $262.79 50+ $251.11 **SMA Male to 1.85mm Male** VSWR 1.3:1 to 18 GHz **Model No: PE9727**	 PRICE 1-9 $243.99 10-24 $231.79 25-49 $219.59 50+ $209.83 **SMA Male to 1.85mm Female** VSWR 1.3:1 to 18 GHz **Model No: PE9728**	 PRECISION PRICE 1-9 $245.99 10-24 $233.69 25-49 $221.39 50+ $211.55 **SMA Male to 2.4mm Male** VSWR 1.2:1 to 26.5 GHz **Model No: PE9653**
5	 PRECISION PRICE 1-9 $243.99 10-24 $231.79 25-49 $219.59 50+ $209.83 **SMA Male to 2.4mm Female** VSWR 1.2:1 to 26.5 GHz **Model No: PE9654**	 PRECISION PRICE 1-9 $253.99 10-24 $241.29 25-49 $228.59 50+ $218.43 **SMA Male to 2.92mm Male** VSWR 1.2:1 to 26.5 GHz **Model No: PE91010**	 PRECISION PRICE 1-9 $247.99 10-24 $235.59 25-49 $223.19 50+ $213.27 **SMA Male to 2.92mm Female** VSWR 1.2:1 to 26.5 GHz **Model No: PE91008**	 PRICE 1-9 $249.99 10-24 $237.49 25-49 $224.99 50+ $214.99 **SMA Male to 3.5mm Male** VSWR 1.25:1 to 18 GHz **Model No: PE9722**	 PRICE 1-9 $193.99 10-24 $184.29 25-49 $174.59 50+ $166.83 **SMA Male to 3.5mm Female** VSWR 1.2:1 to 27 GHz **Model No: PE91536**
6	 PRECISION PRICE 1-4 $620.00 5-9 $589.00 10-24 $558.00 25+ $533.20 **SMA Male to 7mm Sexless** VSWR 1.15:1 to 18 GHz **Model No: PE9215**	 PRICE 1-24 $51.99 25-49 $49.39 50-99 $46.79 100+ $44.71 **SMA Male to BNC Male** Max. Freq. 4 GHz **Model No: PE9072**	 PRICE 1-24 $137.99 25-49 $131.09 50-99 $124.19 100+ $118.67 **SMA Male to BNC Male** VSWR 1.25:1 to 8 GHz **Model No: PE9493**	 PRICE 1-24 $32.99 25-49 $31.34 50-99 $29.69 100+ $28.37 **SMA Male to BNC Female** VSWR 1.3:1 to 4 GHz **Model No: PE9074**	 PRICE 1-9 $171.99 10-24 $163.39 25-49 $154.79 50+ $147.91 **SMA Male to BNC Female** VSWR 1.25:1 to 8 GHz **Model No: PE9495**
7	 PRICE 1-24 $41.59 25-49 $39.51 50-99 $37.43 100+ $35.77 **SMA Male to 75 Ohm F Female** Max. Freq. 2 GHz **Model No: PE91003**	 PRICE 1-24 $27.19 25-49 $25.83 50-99 $24.47 100+ $23.38 **SMA Male to FME Jack** **Model No: PE9707**	 PRICE 1-9 $287.99 10-24 $273.59 25-49 $259.19 50+ $247.67 **SMA Male to GR874 Sexless** **Model No: PE9259**	 PRICE 1-24 $109.99 25-49 $104.49 50-99 $98.99 100+ $94.59 **SMA Male to HN Male** VSWR 1.4:1 to 4 GHz **Model No: PE91448**	 PRICE 1-9 $163.99 10-24 $155.79 25-49 $147.59 50+ $141.03 **SMA Male to HN Female** Max. Freq. 4 GHz **Model No: PE9256**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $133.99 25-49 $127.29 50-99 $120.59 100+ $115.23 **SMA Male to MCX Plug** **Model No:** PE9473	 PRICE 1-24 $121.99 25-49 $115.89 50-99 $109.79 100+ $104.91 **SMA Male to MCX Jack** **Model No:** PE9472	 PRICE 1-24 $105.99 25-49 $100.69 50-99 $95.39 100+ $91.15 **SMA Male to Full Detent Mini SMP Male** VSWR 1.2:1 to 18 GHz **Model No:** PE91302	 PRICE 1-24 $119.99 25-49 $113.99 50-99 $107.99 100+ $103.19 **SMA Male to Smooth Bore Mini SMP Male** VSWR 1.2:1 to 18 GHz **Model No:** PE91303	 PRICE 1-9 $221.99 10-24 $210.89 25-49 $199.79 PRECISION 50+ $190.91 **SMA Male to Full Detent Mini SMP Male** VSWR 1.2:1 to 26.5 GHz **Model No:** PE91052
2	 PRICE 1-24 $107.99 25-49 $102.59 50-99 $97.19 100+ $92.87 **SMA Male to Mini SMP Female** VSWR 1.2:1 to 18 GHz **Model No:** PE91304	 PRICE 1-9 $269.99 10-24 $256.49 25-49 $242.99 PRECISION 50+ $232.19 **SMA Male to Mini SMP Female** VSWR 1.2:1 to 26.5 GHz **Model No:** PE91103	 PRICE 1-9 $291.99 10-24 $277.39 25-49 $262.79 50+ $251.11 **SMA Male to Snap-On MMBX Plug** VSWR 1.2:1 to 12.4 GHz **Model No:** PE91360	 PRICE 1-9 $217.99 10-24 $207.09 25-49 $196.19 50+ $187.47 **SMA Male to Snap-On MMBX Jack** VSWR 1.08:1 to 12.4 GHz **Model No:** PE91362	 PRICE 1-9 $149.99 10-24 $142.49 25-49 $134.99 50+ $128.99 **SMA Male to MMCX Plug** **Model No:** PE9476
3	 PRICE 1-24 $103.99 25-49 $98.79 50-99 $93.59 100+ $89.43 **SMA Male to MMCX Jack** **Model No:** PE9478	 PRICE 1-24 $28.79 25-49 $27.35 50-99 $25.91 100+ $24.76 **SMA Male to N Male** VSWR 1.3:1 to 11 GHz **Model No:** PE9080	 PRICE 1-9 $163.99 10-24 $155.79 25-49 $147.59 PRECISION 50+ $141.03 **SMA Male to N Male** VSWR 1.15:1 to 18 GHz **Model No:** PE9431	 PRICE 1-9 $173.99 10-24 $165.29 25-49 $156.59 PRECISION 50+ $149.63 **SMA Male to N Male** **4 Hole Flange-Mounting Hole A05** VSWR 1.15:1 to 18 GHz **Model No:** PE9499	 PRICE 1-24 $26.99 25-49 $25.64 50-99 $24.29 100+ $23.21 **SMA Male to N Female** VSWR 1.3:1 to 11 GHz **Model No:** PE9082
4	 PRICE 1-24 $121.99 25-49 $115.89 50-99 $109.79 PRECISION 100+ $104.91 **SMA Male to N Female** VSWR 1.15:1 to 18 GHz **Model No:** PE9433	 PRICE 1-9 $217.99 10-24 $207.09 25-49 $196.19 PRECISION 50+ $187.47 **SMA Male to N Female Bulkhead** VSWR 1.15:1 to 18 GHz **Model No:** PE9487	 PRICE 1-24 $119.99 25-49 $113.99 50-99 $107.99 100+ $103.19 **SMA Male to N Female 4 Hole Flange** VSWR 1.4:1 to 18 GHz **Model No:** PE9105	 PRICE 1-9 $235.99 10-24 $224.19 25-49 $212.39 PRECISION 50+ $202.95 **SMA Male to N Female 4 Hole Flange** VSWR 1.15:1 to 18 GHz **Model No:** PE9497	 PRICE 1-9 $191.99 10-24 $182.39 25-49 $172.79 PRECISION 50+ $165.11 **SMA Male to N Female Bulkhead** VSWR 1.15:1 to 18 GHz **Model No:** PE9488
5	 PRICE 1-24 $27.39 25-49 $26.29 50-99 $25.47 100+ $24.92 **Push-On SMA Male to SMA Female** VSWR 1.5:1 to 18 GHz **Model No:** PE91336	 PRICE 1-24 $105.99 25-49 $100.69 50-99 $95.39 100+ $91.15 **SMA Male to SMB Plug** VSWR 1.25:1 to 4 GHz **Model No:** PE9144	 PRICE 1-24 $58.99 25-49 $56.04 50-99 $53.09 100+ $50.73 **SMA Male to SMB Jack** VSWR 1.25:1 to 4 GHz **Model No:** PE9145	 PRICE 1-24 $83.99 25-49 $79.79 50-99 $75.59 100+ $72.23 **SMA Male to SMC Plug** Max. Freq. 10 GHz **Model No:** PE9148	 PRICE 1-24 $71.99 25-49 $68.39 50-99 $64.79 100+ $61.91 **SMA Male to SMC Jack** VSWR 1.2:1 to 10 GHz **Model No:** PE9149
6	 PRICE 1-24 $84.99 25-49 $80.74 50-99 $76.49 100+ $73.09 **SMA Male to Full Detent SMP Male** VSWR 1.2:1 to 18 GHz **Model No:** PE91309	 PRICE 1-24 $82.99 25-49 $78.84 50-99 $74.69 100+ $71.37 **SMA Male to Limited Detent SMP Male** VSWR 1.2:1 to 18 GHz **Model No:** PE91310	 PRICE 1-24 $82.99 25-49 $78.84 50-99 $74.69 100+ $71.37 **SMA Male to Smooth Bore SMP Male** VSWR 1.2:1 to 18 GHz **Model No:** PE91311	 PRICE 1-9 $149.99 10-24 $142.49 25-49 $134.99 PRECISION 50+ $128.99 **SMA Male to Full Detent SMP Male** VSWR 1.2:1 to 26.5 GHz **Model No:** PE91063	 PRICE 1-9 $197.99 10-24 $188.09 25-49 $178.19 PRECISION 50+ $170.27 **SMA Male to Limited Detent SMP Male** VSWR 1.2:1 to 18 GHz **Model No:** PE9511
7	 PRICE 1-24 $84.99 25-49 $80.74 50-99 $76.49 100+ $73.09 **SMA Male to SMP Female** VSWR 1.2:1 to 18 GHz **Model No:** PE91312	 PRICE 1-9 $185.99 10-24 $176.69 25-49 $167.39 PRECISION 50+ $159.95 **SMA Male to SMP Female** VSWR 1.2:1 to 26.5 GHz **Model No:** PE91062	 PRICE 1-9 $225.99 10-24 $214.69 25-49 $203.39 PRECISION 50+ $194.35 **SMA Male to SMP Female** VSWR 1.2:1 to 18 GHz **Model No:** PE9513	 PRICE 1-24 $119.99 25-49 $113.99 50-99 $107.99 100+ $103.19 **SMA Male to SSMA Male** VSWR 1.25:1 to 26.5 GHz **Model No:** PE9187	 PRICE 1-24 $77.99 25-49 $74.09 50-99 $70.19 100+ $67.07 **SMA Male to SSMA Female** VSWR 1.4:1 to 18 GHz **Model No:** PE9063

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $111.99 25-49 $106.39 50-99 $100.79 100+ $96.31 **SMA Male to SSMB Jack** **Model No: PE9401**	 PRICE 1-24 $51.99 25-49 $49.39 50-99 $46.79 100+ $44.71 **SMA Male to TNC Male** VSWR 1.3:1 to 11 GHz **Model No: PE9076**	 PRICE 1-9 $161.99 10-24 $153.89 25-49 $145.79 50+ $139.31 **SMA Male to TNC Male** VSWR 1.25:1 to 18 GHz **Model No: PE9439**	 PRICE 1-24 $54.99 25-49 $52.24 50-99 $49.49 100+ $47.29 **SMA Male to TNC Female** VSWR 1.3:1 to 11 GHz **Model No: PE9078**	 PRICE 1-24 $139.99 25-49 $130.19 50-99 $120.39 100+ $111.99 **SMA Male to TNC Female** VSWR 1.2:1 to 18 GHz **Model No: PE91507**
2	 PRICE 1-24 $113.99 25-49 $108.29 50-99 $102.59 100+ $98.03 **SMA Male to TNC Female** **4 Hole Flange-Mounting Hole A04** VSWR 1.3:1 to 11 GHz **Model No: PE9384**	 PRICE 1-24 $56.99 25-49 $54.14 50-99 $51.29 100+ $49.01 **SMA Male to UHF Female** **Model No: PE9400**	 PRICE 1-24 $36.59 25-49 $34.76 50-99 $32.93 100+ $31.47 **SMA Male to UMCX Jack** VSWR 1.3:1 to 6 GHz **Model No: PE91007**	 PRICE 1-24 $115.99 25-49 $110.19 50-99 $104.39 100+ $99.75 **SMA Female to 1.0/2.3 Plug** **Model No: PE9691**	 PRICE 1-24 $99.99 25-49 $94.99 50-99 $89.99 100+ $85.99 **SMA Female to 1.0/2.3 Jack** **Model No: PE9693**
3	 PRICE 1-9 $247.99 10-24 $235.59 25-49 $223.19 50+ $213.27 **SMA Female to 1.85mm Male** VSWR 1.3:1 to 18 GHz **Model No: PE9726**	 PRICE 1-9 $263.99 10-24 $250.79 25-49 $237.59 50+ $227.03 **SMA Female to 1.85mm Female** VSWR 1.3:1 to 18 GHz **Model No: PE9729**	 PRICE 1-9 $253.99 10-24 $241.29 25-49 $228.59 50+ $218.43 **SMA Female to 2.4mm Male** VSWR 1.2:1 to 27 GHz **Model No: PE9655**	 PRICE 1-9 $265.99 10-24 $252.69 25-49 $239.39 PRECISION 50+ $228.75 **SMA Female to 2.4mm Female** VSWR 1.2:1 to 26.5 GHz **Model No: PE9656**	 PRICE 1-9 $243.99 10-24 $231.79 25-49 $219.59 PRECISION 50+ $209.83 **SMA Female to 2.92mm Male** VSWR 1.2:1 to 26.5 GHz **Model No: PE91009**
4	 PRICE 1-9 $249.99 10-24 $237.49 25-49 $224.99 PRECISION 50+ $214.99 **SMA Female to 2.92mm Female** VSWR 1.2:1 to 26.5 GHz **Model No: PE91011**	 PRICE 1-9 $227.99 10-24 $216.59 25-49 $205.19 50+ $196.07 **SMA Female to 3.5mm Male** VSWR 1.2:1 to 27 GHz **Model No: PE9724**	 PRICE 1-9 $253.99 10-24 $241.29 25-49 $228.59 50+ $218.43 **SMA Female to 3.5mm Female** VSWR 1.2:1 to 27 GHz **Model No: PE9725**	 PRICE 1-9 $271.99 10-24 $258.39 25-49 $244.79 PRECISION 50+ $233.91 **SMA Female to 7mm Sexless** VSWR 1.15:1 to 18 GHz **Model No: PE9214**	 PRICE 1-4 $680.00 5-9 $646.00 10-24 $612.00 PRECISION 25+ $584.80 **SMA Female to 7mm Sexless** **4 Hole Flange-Mounting Hole A05** VSWR 1.15:1 to 18 GHz **Model No: PE9327**
5	 PRICE 1-24 $107.99 25-49 $102.59 50-99 $97.19 Low PIM 100+ $92.87 **SMA Female to 7/16 DIN Male** VSWR 1.09:1 to 7.5 GHz **Model No: PE91036**	 PRICE 1-9 $133.99 10-24 $127.29 25-49 $120.59 50+ $115.23 **SMA Female to 7/16 DIN Male** VSWR 1.25:1 to 6 GHz **Model No: PE91175**	 PRICE 1-24 $107.99 25-49 $102.59 50-99 $97.19 Low PIM 100+ $92.87 **SMA Female to 7/16 DIN Female** Max. Freq. 8 GHz **Model No: PE91042**	 PRICE 1-24 $24.99 25-49 $23.74 50-99 $22.49 100+ $21.49 **SMA Female to BNC Male** VSWR 1.3:1 to 4 GHz **Model No: PE9073**	 PRICE 1-24 $90.99 25-49 $86.44 50-99 $81.89 100+ $78.25 **SMA Female to BNC Male** VSWR 1.25:1 to 8 GHz **Model No: PE9494**
6	 PRICE 1-24 $53.99 25-49 $51.29 50-99 $48.59 100+ $46.43 **SMA Female to BNC Female** VSWR 1.3:1 to 4 GHz **Model No: PE9075**	 PRICE 1-24 $133.99 25-49 $127.29 50-99 $120.59 100+ $115.23 **SMA Female to BNC Female** VSWR 1.25:1 to 8 GHz **Model No: PE9496**	 PRICE 1-24 $60.99 25-49 $57.94 50-99 $54.89 100+ $52.45 **SMA Female to BNC Female Bulkhead** Max. Freq. 4 GHz **Model No: PE9185**	 PRICE 1-24 $76.99 25-49 $73.14 50-99 $69.29 100+ $66.21 **SMA Female to BNC Female Bulkhead** Max. Freq. 4 GHz **Model No: PE9407**	 PRICE 1-24 $30.79 25-49 $29.25 50-99 $27.71 100+ $26.48 **SMA Female to 75 Ohm F Male** VSWR 1.5:1 to 500 MHz **Model No: PE91045**
7	 PRICE 1-24 $65.99 25-49 $62.69 50-99 $59.39 100+ $56.75 **SMA Female to 75 Ohm F Female** **Model No: PE91002**	 PRICE 1-24 $25.19 25-49 $23.93 50-99 $22.67 100+ $21.66 **SMA Female to FME Plug** **Model No: PE9703**	 PRICE 1-24 $32.39 25-49 $30.77 50-99 $29.15 100+ $27.86 **SMA Female to FME Jack** VSWR 1.3:1 to 900 MHz **Model No: PE9708**	 PRICE 1-9 $215.99 10-24 $205.19 25-49 $194.39 50+ $185.75 **SMA Female to GR874 Sexless** **Model No: PE9260**	 PRICE 1-24 $98.99 25-49 $94.04 50-99 $89.09 100+ $85.13 **SMA Female to HN Male** Max. Freq. 4 GHz **Model No: PE9253**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $80.99 25-49 $76.94 50-99 $72.89 100+ $69.65 **SMA Female to HN Female** Max. Freq. 4 GHz **Model No: PE9255**	 PRICE 1-24 $96.99 25-49 $92.14 50-99 $87.29 100+ $83.41 **SMA Female to MCX Plug** Max. Freq. 6 GHz **Model No: PE9471**	 PRICE 1-24 $95.99 25-49 $91.19 50-99 $86.39 100+ $82.55 **SMA Female to MCX Jack** **Model No: PE9470**	 PRICE 1-24 $107.99 25-49 $102.59 50-99 $97.19 100+ $92.87 **SMA Female to Full Detent Mini SMP Male** VSWR 1.2:1 to 18 GHz **Model No: PE91299**	 PRICE 1-24 $119.99 25-49 $113.99 50-99 $107.99 100+ $103.19 **SMA Female to Smooth Bore Mini SMP Male** VSWR 1.2:1 to 18 GHz **Model No: PE91300**
2	 PRICE 1-9 $203.99 10-24 $193.79 25-49 $183.59 50+ $175.43 **SMA Female to Full Detent Mini SMP Male** VSWR 1.2:1 to 26.5 GHz **Model No: PE91129**	 PRICE 1-24 $105.99 25-49 $100.69 50-99 $95.39 100+ $91.15 **SMA Female to Mini SMP Female** VSWR 1.2:1 to 18 GHz **Model No: PE91301**	 PRECISION PRICE 1-9 $183.99 10-24 $174.79 25-49 $165.59 50+ $158.23 **SMA Female to Mini SMP Female** VSWR 1.2:1 to 26.5 GHz **Model No: PE91051**	 PRICE 1-9 $231.99 10-24 $220.39 25-49 $208.79 50+ $199.51 **SMA Female to Snap-On MMBX Plug** VSWR 1.08:1 to 12.4 GHz **Model No: PE91361**	 PRICE 1-9 $207.99 10-24 $197.59 25-49 $187.19 50+ $178.87 **SMA Female to Snap-On MMBX Jack** VSWR 1.08:1 to 12.4 GHz **Model No: PE91363**
3	 PRICE 1-24 $109.99 25-49 $104.49 50-99 $98.99 100+ $94.59 **SMA Female to MMCX Plug** **Model No: PE9475**	 PRICE 1-24 $97.99 25-49 $93.09 50-99 $88.19 100+ $84.27 **SMA Female to MMCX Jack** **Model No: PE9477**	 PRICE 1-24 $22.59 25-49 $21.46 50-99 $20.33 100+ $19.43 **SMA Female to N Male** VSWR 1.3:1 to 11 GHz **Model No: PE9081**	 PRICE 1-9 $241.99 10-24 $229.89 25-49 $217.79 50+ $208.11 **SMA Female to QD N Male** **Model No: PE9684**	 PRICE 1-24 $83.99 25-49 $79.79 50-99 $75.59 100+ $72.23 **SMA Female to N Male Bulkhead** Max. Freq. 11 GHz **Model No: PE9551**
4	 PRICE 1-24 $119.99 25-49 $113.99 50-99 $107.99 100+ $103.19 **SMA Female to N Male 4 Hole Flange-Mounting Hole A05** VSWR 1.2:1 to 12.4 GHz **Model No: PE9275**	 PRECISION PRICE 1-9 $207.99 10-24 $197.59 25-49 $187.19 50+ $178.87 **SMA Female to N Male 4 Hole Flange-Mounting Hole A05** VSWR 1.15:1 to 18 GHz **Model No: PE9498**	 PRICE 1-24 $24.99 25-49 $23.74 50-99 $22.49 100+ $21.49 **SMA Female to N Female** VSWR 1.3:1 to 11 GHz **Model No: PE9083**	 PRECISION PRICE 1-24 $119.99 25-49 $113.99 50-99 $107.99 100+ $103.19 **SMA Female to N Female** VSWR 1.15:1 to 18 GHz **Model No: PE9432**	 PRICE 1-24 $29.39 25-49 $27.92 50-99 $26.45 100+ $25.28 **SMA Female to N Female Bulkhead** VSWR 1.3:1 to 11 GHz **Model No: PE9252**
5	 PRECISION PRICE 1-9 $185.99 10-24 $176.69 25-49 $167.39 50+ $159.95 **SMA Female to N Female Bulkhead** VSWR 1.15:1 to 18 GHz **Model No: PE9486**	 PRICE 1-24 $68.99 25-49 $65.54 50-99 $62.09 100+ $59.33 **SMA Female to N Female 4 Hole Flange-Mounting Hole A05** VSWR 1.3:1 to 11 GHz **Model No: PE9104**	 PRECISION PRICE 1-9 $173.99 10-24 $165.29 25-49 $156.59 50+ $149.63 **SMA Female to N Female 4 Hole Flange-Mounting Hole A05** VSWR 1.15:1 to 18 GHz **Model No: PE9434**	 PRICE 1-24 $88.99 25-49 $84.54 50-99 $80.09 100+ $76.53 **SMA Female to N Female Bulkhead** VSWR 1.25:1 to 6 GHz **Model No: PE9408**	 PRECISION PRICE 1-9 $191.99 10-24 $182.39 25-49 $172.79 50+ $165.11 **SMA Female to N Female Bulkhead-Mounting Hole G01** VSWR 1.15:1 to 18 GHz **Model No: PE9435**
6	 PRICE 1-24 $75.99 25-49 $72.19 50-99 $68.39 100+ $65.35 **SMA Female to QMA Male** Max. Freq. 18 GHz **Model No: PE9786**	 PRICE 1-24 $32.99 25-49 $31.34 50-99 $29.69 100+ $28.37 **SMA Female to SMB Plug** VSWR 1.3:1 to 4 GHz **Model No: PE9142**	 PRICE 1-24 $68.99 25-49 $65.54 50-99 $62.09 100+ $59.33 **SMA Female to SMB Jack** VSWR 1.46:1 to 4 GHz **Model No: PE9143**	 PRICE 1-24 $66.99 25-49 $63.64 50-99 $60.29 100+ $57.61 **SMA Female to SMC Plug** VSWR 1.2:1 to 10 GHz **Model No: PE9146**	 PRICE 1-24 $71.99 25-49 $68.39 50-99 $64.79 100+ $61.91 **SMA Female to SMC Jack** Max. Freq. 10 GHz **Model No: PE9147**
7	 PRICE 1-24 $85.99 25-49 $81.69 50-99 $77.39 100+ $73.95 **SMA Female to Full Detent SMP Male** VSWR 1.2:1 to 18 GHz **Model No: PE91305**	 PRICE 1-24 $84.99 25-49 $80.74 50-99 $76.49 100+ $73.09 **SMA Female to Limited Detent SMP Male** VSWR 1.2:1 to 18 GHz **Model No: PE91306**	 PRICE 1-24 $103.99 25-49 $98.79 50-99 $93.59 100+ $89.43 **SMA Female to Smooth Bore SMP Male** VSWR 1.2:1 to 18 GHz **Model No: PE91307**	 PRECISION PRICE 1-9 $145.99 10-24 $138.69 25-49 $131.39 50+ $125.55 **SMA Female to Limited Detent SMP Male** VSWR 1.2:1 to 26.5 GHz **Model No: PE91050**	 PRECISION PRICE 1-9 $143.99 10-24 $136.79 25-49 $129.59 50+ $123.83 **SMA Female to Full Detent SMP Male** VSWR 1.2:1 to 26.5 GHz **Model No: PE91056**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRECISION 1-9 $211.99 10-24 $201.39 25-49 $190.79 50+ $182.31 **SMA Female to Limited Detent SMP Male** VSWR 1.2:1 to 18 GHz **Model No:** PE9512	 1-9 $479.99 10-24 $455.99 25-49 $431.99 50+ $412.79 **SMA Female to Limited Detent SMP Male** Max. Freq. 26.5 GHz **Model No:** PE9778	 1-9 $171.99 10-24 $163.39 25-49 $154.79 50+ $147.91 **SMA Female to Full Detent SMP Male Bulkhead-Mounting Hole F05** VSWR 1.3:1 to 26.5 GHz **Model No:** PE91054	 PRECISION 1-9 $145.99 10-24 $138.69 25-49 $131.39 50+ $125.55 **SMA Female to SMP Male 2 Hole Flange-Mounting Hole C05** VSWR 1.2:1 to 26.5 GHz **Model No:** PE91057	 PRECISION 1-9 $145.99 10-24 $138.69 25-49 $131.39 50+ $125.55 **SMA Female to Full Detent SMP Male 2 Hole Flange-Mounting Hole C01** VSWR 1.2:1 to 26.5 GHz **Model No:** PE91058
2	 PRECISION 1-9 $141.99 10-24 $134.89 25-49 $127.79 50+ $122.11 **SMA Female to Smooth Bore SMP Male 2 Hole Flange-Mounting Hole C05** VSWR 1.2:1 to 26.5 GHz **Model No:** PE91061	 PRECISION 1-9 $159.99 10-24 $151.99 25-49 $143.99 50+ $137.59 **SMA Female to Limited Detent SMP Male 2 Hole Flange-Mounting Hole C05** VSWR 1.2:1 to 26.5 GHz **Model No:** PE91066	 PRECISION 1-9 $169.99 10-24 $161.49 25-49 $152.99 50+ $146.19 **SMA Female to SMP Male 4 Hole Flange-Mounting Hole A01** VSWR 1.2:1 to 26.5 GHz **Model No:** PE91059	 1-24 $82.99 25-49 $78.84 50-99 $74.69 100+ $71.37 **SMA Female to SMP Female** VSWR 1.2:1 to 18 GHz **Model No:** PE91308	 PRECISION 1-9 $143.99 10-24 $136.79 25-49 $129.59 50+ $123.83 **SMA Female to SMP Female** VSWR 1.2:1 to 26.5 GHz **Model No:** PE91064
3	 PRECISION 1-9 $259.99 10-24 $246.99 25-49 $233.99 50+ $223.59 **SMA Female to SMP Female** VSWR 1.2:1 to 18 GHz **Model No:** PE9779	 1-24 $63.99 25-49 $60.79 50-99 $57.59 100+ $55.03 **SMA Female to SSMA Male** VSWR 1.3:1 to 18 GHz **Model No:** PE9188	 1-24 $83.99 25-49 $79.79 50-99 $75.59 100+ $72.23 **SMA Female to SSMA Female** VSWR 1.4:1 to 18 GHz **Model No:** PE9399	 1-24 $74.99 25-49 $71.24 50-99 $67.49 100+ $64.49 **SMA Female to SSMB Plug** **Model No:** PE9402	 1-24 $68.99 25-49 $65.54 50-99 $62.09 100+ $59.33 **SMA Female to SSMC Plug** VSWR 1.25:1 to 3 GHz **Model No:** PE91380
4	 1-24 $69.99 25-49 $66.49 50-99 $62.99 100+ $60.19 **SMA Female to SSMC Jack** VSWR 1.25:1 to 3 GHz **Model No:** PE91433	 1-24 $25.19 25-49 $23.93 50-99 $22.67 100+ $21.66 **SMA Female to TNC Male** VSWR 1.3:1 to 11 GHz **Model No:** PE9077	 1-9 $137.99 10-24 $131.09 25-49 $124.19 50+ $118.67 **SMA Female to TNC Male** VSWR 1.25:1 to 18 GHz **Model No:** PE9440	 1-24 $57.99 25-49 $55.09 50-99 $52.19 100+ $49.87 **SMA Female to TNC Female** Max. Freq. 11 GHz **Model No:** PE9079	 1-9 $177.99 10-24 $169.09 25-49 $160.19 50+ $153.07 **SMA Female to TNC Female** VSWR 1.25:1 to 18 GHz **Model No:** PE9442
5	 1-24 $59.99 25-49 $56.99 50-99 $53.99 100+ $51.59 **SMA Female to TNC Female Bulkhead-Mounting Hole B05** VSWR 1.3:1 to 11 GHz **Model No:** PE9251	 1-24 $62.99 25-49 $59.84 50-99 $56.69 100+ $54.17 **SMA Female to TNC Female 4 Hole Flange-Mounting Hole A03** Max. Freq. 11 GHz **Model No:** PE9276	 1-24 $67.99 25-49 $64.59 50-99 $61.19 100+ $58.47 **SMA Female to UHF Male** VSWR 1.3:1 to 300 MHz **Model No:** PE9415	 1-24 $27.79 25-49 $26.40 50-99 $25.01 100+ $23.90 **SMA Female to UMCX Plug** VSWR 1.3:1 to 6 GHz **Model No:** PE91005	 1-24 $34.59 25-49 $32.86 50-99 $31.13 100+ $29.75 **SMA Female to UMCX Jack** VSWR 1.3:1 to 6 GHz **Model No:** PE91006
6	***Reverse Polarity SMA In-Series*** →	 1-24 $48.19 25-49 $45.78 50-99 $43.37 100+ $41.44 **SMA Male to Rev. Pol. SMA Male** VSWR 1.2:1 to 18 GHz **Model No:** PE91259	 1-24 $80.99 25-49 $76.94 50-99 $72.89 100+ $69.65 **QD SMA Male to Rev. Pol. SMA Female** VSWR 1.25:1 to 18 GHz **Model No:** PE91265	 1-24 $49.79 25-49 $47.30 50-99 $44.81 100+ $42.82 **SMA Male to Rev. Pol. SMA Female** VSWR 1.25:1 to 18 GHz **Model No:** PE9534	 1-24 $54.99 25-49 $52.24 50-99 $49.49 100+ $47.29 **SMA Male to Rev. Pol. SMA Female Right Angle** VSWR 1.23:1 to 12.4 GHz **Model No:** PE91264
7	 1-24 $27.79 25-49 $26.40 50-99 $25.01 100+ $23.90 **SMA Female to Rev. Pol. SMA Male** VSWR 1.25:1 to 18 GHz **Model No:** PE9533	 1-24 $44.19 25-49 $41.98 50-99 $39.77 100+ $38.00 **SMA Female to Rev. Pol. SMA Female** VSWR 1.2:1 to 18 GHz **Model No:** PE91260	 1-24 $133.99 25-49 $127.29 50-99 $120.59 100+ $115.23 **QD Rev. Pol. SMA Male to SMA Male** VSWR 1.25:1 to 18 GHz **Model No:** PE91266	 1-24 $88.99 25-49 $84.54 50-99 $80.09 100+ $76.53 **QD Rev. Pol. SMA Male to SMA Female** VSWR 1.25:1 to 18 GHz **Model No:** PE91267	 1-24 $45.19 25-49 $42.93 50-99 $40.67 100+ $38.86 **Rev. Pol. SMA Male to SMA Female Right Angle** VSWR 1.23:1 to 12.4 GHz **Model No:** PE91263

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $53.99 25-49 $51.29 50-99 $48.59 100+ $46.43 **Rev. Pol. SMA Male to Rev. Pol. SMA Male** VSWR 1.2:1 to 18 GHz **Model No: PE91261**	 PRICE 1-24 $65.99 25-49 $62.69 50-99 $59.39 100+ $56.75 **Rev. Pol. SMA Male to Rev. Pol. SMA Male** VSWR 1.35:1 to 6 GHz **Model No: PE91330**	 PRICE 1-24 $80.99 25-49 $76.94 50-99 $72.89 100+ $69.65 **QD Rev. Pol. SMA Male to Rev. Pol. SMA Female** VSWR 1.25:1 to 18 GHz **Model No: PE91268**	 PRICE 1-24 $65.99 25-49 $62.69 50-99 $59.39 100+ $56.75 **Rev. Pol. SMA Male to Rev. Pol. SMA Female** VSWR 1.35:1 to 6 GHz **Model No: PE91331**	 PRICE 1-24 $44.19 25-49 $41.98 50-99 $39.77 100+ $38.00 **Rev. Pol. SMA Male to Rev. Pol. SMA Female Right Angle** VSWR 1.25:1 to 6 GHz **Model No: PE9594**
2	 PRICE 1-24 $53.99 25-49 $51.29 50-99 $48.59 100+ $46.43 **Rev. Pol. SMA Female to Rev. Pol. SMA Female** VSWR 1.2:1 to 18 GHz **Model No: PE91262**	 PRICE 1-24 $43.39 25-49 $41.22 50-99 $39.05 100+ $37.32 **Rev. Pol. SMA Female to Rev. Pol. SMA Female** VSWR 1.35:1 to 6 GHz **Model No: PE91334**	 PRICE 1-24 $62.99 25-49 $59.84 50-99 $56.69 100+ $54.17 **Rev. Pol. SMA Female to Rev. Pol. SMA Female Bulkhead-Mounting Hole B02** VSWR 1.25:1 to 18 GHz **Model No: PE9593**	 PRICE 1-24 $54.99 25-49 $52.24 50-99 $49.49 100+ $47.29 **Rev. Pol. SMA Female to Rev. Pol. SMA Female 2 Hole Flange** VSWR 1.2:1 to 18 GHz **Model No: PE91270**	 PRICE 1-24 $62.99 25-49 $59.84 50-99 $56.69 100+ $54.17 **Rev. Pol. SMA Female to Rev. Pol. SMA Female 4 Hole Flange** VSWR 1.2:1 to 18 GHz **Model No: PE91269**
3	***Reverse Polarity SMA Between Series*** →	 PRICE 1-24 $96.99 25-49 $92.14 50-99 $87.29 100+ $83.41 **SMA Male to Rev. Pol. MCX Plug** VSWR 1.2:1 to 6 GHz **Model No: PE9581**	 PRICE 1-24 $68.99 25-49 $65.54 50-99 $62.09 100+ $59.33 **SMA Male to Rev. Pol. TNC Female** VSWR 1.25:1 to 11 GHz **Model No: PE9600**	 PRICE 1-24 $65.99 25-49 $62.69 50-99 $59.39 100+ $56.75 **SMA Female to Rev. Pol. TNC Male** Max. Freq. 11 GHz **Model No: PE9602**	 PRICE 1-24 $94.99 25-49 $90.24 50-99 $85.49 100+ $81.69 **SMA Female to Rev. Pol. TNC Female** VSWR 1.25:1 to 11 GHz **Model No: PE9603**
4	 PRICE 1-24 $90.99 25-49 $86.44 50-99 $81.89 100+ $78.25 **Rev. Pol. SMA Male to N Female** VSWR 1.25:1 to 11 GHz **Model No: PE9732**	 PRICE 1-24 $76.99 25-49 $73.14 50-99 $69.29 100+ $66.21 **Rev. Pol. SMA Male to TNC Male** VSWR 1.2:1 to 11 GHz **Model No: PE9597**	 PRICE 1-24 $73.99 25-49 $70.29 50-99 $66.59 100+ $63.63 **Rev. Pol. SMA Male to TNC Female** VSWR 1.2:1 to 11 GHz **Model No: PE9596**	 PRICE 1-24 $99.99 25-49 $94.99 50-99 $89.99 100+ $85.99 **Rev. Pol. SMA Female to N Male** VSWR 1.25:1 to 11 GHz **Model No: PE9733**	 PRICE 1-24 $75.99 25-49 $72.19 50-99 $68.39 100+ $65.35 **Rev. Pol. SMA Female to TNC Male** VSWR 1.2:1 to 11 GHz **Model No: PE9598**
5	 PRICE 1-24 $75.99 25-49 $72.19 50-99 $68.39 100+ $65.35 **Rev. Pol. SMA Female to TNC Female** VSWR 1.2:1 to 11 GHz **Model No: PE9599**	 PRICE 1-24 $76.99 25-49 $73.14 50-99 $69.29 100+ $66.21 **Rev. Pol. SMA Male to Rev. Pol. TNC Male** VSWR 1.2:1 to 11 GHz **Model No: PE9605**	 PRICE 1-24 $90.99 25-49 $86.44 50-99 $81.89 100+ $78.25 **Rev. Pol. SMA Male to Rev. Pol. TNC Female** VSWR 1.25:1 to 11 GHz **Model No: PE9604**	 PRICE 1-24 $75.99 25-49 $72.19 50-99 $68.39 100+ $65.35 **Rev. Pol. SMA Female to Rev. Pol. TNC Male** VSWR 1.2:1 to 11 GHz **Model No: PE9607**	 PRICE 1-24 $76.99 25-49 $73.14 50-99 $69.29 100+ $66.21 **Rev. Pol. SMA Female to Rev. Pol. TNC Female** VSWR 1.25:1 to 11 GHz **Model No: PE9606**
6	***Reverse Thread SMA In-Series*** →	 PRICE 1-24 $62.99 25-49 $59.84 50-99 $56.69 100+ $54.17 **SMA Male to Reverse Thread SMA Female** **Model No: PE9682**	 PRICE 1-24 $72.99 25-49 $69.34 50-99 $65.69 100+ $62.77 **SMA Female to Reverse Thread SMA Male** **Model No: PE9683**	***SMB In-Series*** →	 PRICE 1-24 $46.39 25-49 $44.07 50-99 $41.75 100+ $39.90 **SMB Plug to SMB Plug** Max. Freq. 4 GHz **Model No: PE9118**
7	 PRICE 1-24 $135.99 25-49 $129.19 50-99 $122.39 100+ $116.95 **SMB Plug to SMB Plug Tee** Max. Freq. 4 GHz **Model No: PE9310**	 PRICE 1-24 $73.99 25-49 $70.29 50-99 $66.59 100+ $63.63 **SMB Plug to SMB Jack** VSWR 1.2:1 to 4 GHz **Model No: PE9120**	 PRICE 1-24 $88.99 25-49 $84.54 50-99 $80.09 100+ $76.53 **SMB Plug to SMB Jack Tee** **Model No: PE9309**	 PRICE 1-24 $53.99 25-49 $51.29 50-99 $48.59 100+ $46.43 **SMB Jack to SMB Plug Tee** Max. Freq. 100 MHz **Model No: PE9243**	 PRICE 1-24 $63.99 25-49 $60.79 50-99 $57.59 100+ $55.03 **SMB Jack to SMB Jack** VSWR 1.3:1 to 4 GHz **Model No: PE9116**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $63.99 25-49 $60.79 50-99 $57.59 100+ $55.03 **SMB Jack to SMB Jack Tee** **Model No:** PE9302	 PRICE 1-24 $43.79 25-49 $41.60 50-99 $39.41 100+ $37.66 **SMB Jack to SMB Jack Bulkhead-Mounting Hole B01** Max. Freq. 4 GHz **Model No:** PE9122	***SMB Between Series*** →	 PRICE 1-24 $71.99 25-49 $68.39 50-99 $64.79 100+ $61.91 **SMB Plug to BNC Male** Max. Freq. 4 GHz **Model No:** PE9135	 PRICE 1-24 $75.99 25-49 $72.19 50-99 $68.39 100+ $65.35 **SMB Plug to BNC Female** VSWR 1.3:1 to 4 GHz **Model No:** PE9137
2	 PRICE 1-24 $63.99 25-49 $60.79 50-99 $57.59 100+ $55.03 **SMB Plug to BNC Female Bulkhead-Mounting Hole B05** Max. Freq. 3 GHz **Model No:** PE9241	 PRICE 1-24 $64.99 25-49 $61.74 50-99 $58.49 100+ $55.89 **SMB Jack to BNC Male** Max. Freq. 4 GHz **Model No:** PE9132	 PRICE 1-24 $74.99 25-49 $71.24 50-99 $67.49 100+ $64.49 **SMB Jack to BNC Female** Max. Freq. 4 GHz **Model No:** PE9136	 PRICE 1-24 $66.99 25-49 $63.64 50-99 $60.29 100+ $57.61 **SMB Jack to BNC Female Bulkhead** VSWR 1.3:1 to 4 GHz **Model No:** PE9240	***SMC In-Series*** →
3	 PRICE 1-24 $41.99 25-49 $39.89 50-99 $37.79 100+ $36.11 **SMC Plug to SMC Plug** Max. Freq. 6 GHz **Model No:** PE9117	 PRICE 1-24 $71.99 25-49 $68.39 50-99 $64.79 100+ $61.91 **SMC Plug to SMC Plug Tee** **Model No:** PE9305	 PRICE 1-24 $62.99 25-49 $59.84 50-99 $56.69 100+ $54.17 **SMC Plug to SMC Jack** VSWR 1.2:1 to 10 GHz **Model No:** PE9119	 PRICE 1-24 $78.99 25-49 $75.04 50-99 $71.09 100+ $67.93 **SMC Plug to SMC Jack Right Angle** **Model No:** PE9303	 PRICE 1-24 $56.99 25-49 $54.14 50-99 $51.29 100+ $49.01 **SMC Jack to SMC Plug Tee** Max. Freq. 100 MHz **Model No:** PE9242
4	 PRICE 1-24 $82.99 25-49 $78.84 50-99 $74.69 100+ $71.37 **SMC Jack to SMC Jack Tee** **Model No:** PE9304	 PRICE 1-24 $42.99 25-49 $40.84 50-99 $38.69 100+ $36.97 **SMC Jack to SMC Jack Bulkhead-Mounting Hole B01** Max. Freq. 10 GHz **Model No:** PE91403	***SMC Between Series*** →	 PRICE 1-24 $72.99 25-49 $69.34 50-99 $65.69 100+ $62.77 **SMC Plug to BNC Male** **Model No:** PE9139	 PRICE 1-24 $71.99 25-49 $68.39 50-99 $64.79 100+ $61.91 **SMC Plug to BNC Female** VSWR 1.3:1 to 4 GHz **Model No:** PE9141
5	 PRICE 1-24 $107.99 25-49 $102.59 50-99 $97.19 100+ $92.87 **SMC Plug to SMB Plug** **Model No:** PE9281	 PRICE 1-24 $54.99 25-49 $52.24 50-99 $49.49 100+ $47.29 **SMC Plug to SMB Jack** **Model No:** PE9284	 PRICE 1-24 $71.99 25-49 $68.39 50-99 $64.79 100+ $61.91 **SMC Jack to BNC Male** **Model No:** PE9138	 PRICE 1-24 $83.99 25-49 $79.79 50-99 $75.59 100+ $72.23 **SMC Jack to BNC Female** VSWR 1.35:1 to 4 GHz **Model No:** PE9140	 PRICE 1-24 $98.99 25-49 $94.04 50-99 $89.09 100+ $85.13 **SMC Jack to BNC Female Bulkhead** **Model No:** PE9108
6	 PRICE 1-24 $69.99 25-49 $66.49 50-99 $62.99 100+ $60.19 **SMC Jack to SMB Plug** **Model No:** PE9282	 PRICE 1-24 $71.99 25-49 $68.39 50-99 $64.79 100+ $61.91 **SMC Jack to SMB Jack** **Model No:** PE9283	***SMP In-Series*** →	 PRICE 1-24 $27.79 25-49 $26.40 50-99 $25.01 100+ $23.90 **SMP Female to SMP Female** VSWR 1.2:1 to 12 GHz **Model No:** PE91102	 PRICE 1-24 $93.99 25-49 $89.29 50-99 $84.59 100+ $80.83 **SMP Female to SMP Female** Max. Freq. 26.5 GHz **Model No:** PE9776
7	 PRICE 1-24 $28.39 25-49 $26.97 50-99 $25.55 100+ $24.42 **SMP Female to SMP Female** VSWR 1.2:1 to 8 GHz **Model No:** PE91068	 PRICE 1-24 $42.79 25-49 $40.65 50-99 $38.51 100+ $36.80 **SMP Female to SMP Female** Max. Freq. 40 GHz **Model No:** PE91072	 PRICE 1-24 $43.19 25-49 $41.03 50-99 $38.87 100+ $37.14 **SMP Female to SMP Female** Max. Freq. 40 GHz **Model No:** PE91099	 PRICE 1-24 $18.79 25-49 $17.85 50-99 $16.91 100+ $16.16 **SMP Female to SMP Female** VSWR 1.2:1 to 8 GHz **Model No:** PE91101	 PRICE 1-24 $86.99 25-49 $82.64 50-99 $78.29 100+ $74.81 **SMP Female to SMP Female** Max. Freq. 26.5 GHz **Model No:** PE9775

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $55.99 25-49 $53.19 50-99 $50.39 100+ $48.15 **SMP Female to SMP Female** Max. Freq. 26.5 GHz **Model No: PE9777**	***SMP Between Series***	 PRICE 1-24 $16.39 25-49 $15.57 50-99 $14.75 100+ $14.10 **Push-On SMP Female to Snap-On MMBX Plug** VSWR 1.25:1 to 6 GHz **Model No: PE91364**	 PRICE 1-24 $34.99 25-49 $33.24 50-99 $31.49 100+ $30.09 **SMP Female to SMP Female** Max. Freq. 40 GHz **Model No: PE91065**	***SSMA In-Series***
2	 PRICE 1-9 $141.99 10-24 $134.89 25-49 $127.79 50+ $122.11 **SSMA Male to SSMA Male** **Model No: PE9357**	 PRICE 1-24 $90.99 25-49 $86.44 50-99 $81.89 100+ $78.25 **SSMA Male to SSMA Female** **Model No: PE9358**	 PRICE 1-9 $211.99 10-24 $201.39 25-49 $190.79 50+ $182.31 **QD SSMA Male to SSMA Female** **Model No: PE9685**	 PRICE 1-24 $111.99 25-49 $106.39 50-99 $100.79 100+ $96.31 **SSMA Male to SSMA Female Right Angle** VSWR 1.3:1 to 18 GHz **Model No: PE9334**	 PRICE 1-24 $79.99 25-49 $75.99 50-99 $71.99 100+ $68.79 **SSMA Female to SSMA Female** VSWR 1.3:1 to 25 GHz **Model No: PE9192**
3	 PRICE 1-24 $83.99 25-49 $79.79 50-99 $75.59 100+ $72.23 **SSMA Female to SSMA Female Bulkhead-Mounting Hole B01** **Model No: PE9189**	***SSMA Between Series***	 PRICE 1-9 $155.99 10-24 $148.19 25-49 $140.39 50+ $134.15 **SSMA Male to BNC Male** Max. Freq. 4 MHz **Model No: PE9213**	 PRICE 1-24 $139.99 25-49 $132.99 50-99 $125.99 100+ $120.39 **SSMA Male to BNC Female** **Model No: PE91046**	 PRICE 1-24 $123.99 25-49 $117.79 50-99 $111.59 100+ $106.63 **SSMA Male to N Male** Max. Freq. 11 GHz **Model No: PE9351**
4	 PRICE 1-24 $123.99 25-49 $119.03 50-99 $115.31 100+ $112.83 **SSMA Female to BNC Male** **Model No: PE9191**	 PRICE 1-24 $109.99 25-49 $104.49 50-99 $98.99 100+ $94.59 **SSMA Female to N Male** **Model No: PE9352**	 PRICE 1-24 $101.99 25-49 $96.89 50-99 $91.79 100+ $87.71 **SSMA Female to N Female** **Model No: PE9354**	***SSMB Between Series***	 PRICE 1-24 $109.99 25-49 $104.49 50-99 $98.99 100+ $94.59 **SSMB Plug to BNC Male** **Model No: PE9393**
5	 PRICE 1-24 $135.99 25-49 $129.19 50-99 $122.39 100+ $116.95 **SSMB Plug to BNC Female** **Model No: PE9395**	 PRICE 1-24 $139.99 25-49 $132.99 50-99 $125.99 100+ $120.39 **SSMB Jack to BNC Female** **Model No: PE9394**	***SSMC In-Series***	 PRICE 1-24 $66.99 25-49 $64.31 50-99 $62.30 100+ $60.96 **SSMC Plug to SSMC Plug** VSWR 1.25:1 to 12 GHz **Model No: PE91436**	 PRICE 1-24 $66.99 25-49 $63.64 50-99 $60.29 100+ $57.61 **SSMC Plug to SSMC Jack** VSWR 1.25:1 to 12 GHz **Model No: PE91434**
6	 PRICE 1-24 $66.99 25-49 $63.64 50-99 $60.29 100+ $57.61 **SSMC Jack to SSMC Jack Bulkhead** VSWR 1.25:1 to 4 GHz **Model No: PE91432**	***TNC In-Series***	 PRICE 1-24 $78.99 25-49 $75.04 50-99 $71.09 Low PIM 100+ $67.93 **TNC Male to TNC Male** VSWR 1.25:1 to 6 GHz **Model No: PE91172**	 PRICE 1-24 $67.99 25-49 $64.59 50-99 $61.19 100+ $58.47 **TNC Male to TNC Male** VSWR 1.2:1 to 6 GHz **Model No: PE91202**	 PRICE 1-24 $66.99 25-49 $63.64 50-99 $60.29 100+ $57.61 **TNC Male to TNC Male** VSWR 1.3:1 to 6 GHz **Model No: PE91239**
7	 PRICE 1-24 $44.39 25-49 $42.17 50-99 $39.95 100+ $38.18 **TNC Male to TNC Male** VSWR 1.3:1 to 1,000 MHz **Model No: PE9091**	 PRICE 1-9 $195.99 10-24 $186.19 25-49 $176.39 50+ $168.55 **TNC Male to TNC Male** VSWR 1.25:1 to 18 GHz **Model No: PE9445**	 PRICE 1-24 $119.99 25-49 $113.99 50-99 $107.99 100+ $103.19 **TNC Male to TNC Male Right Angle** Max. Freq. 11 GHz **Model No: PE9560**	 PRICE 1-24 $67.99 25-49 $64.59 50-99 $61.19 100+ $58.47 **TNC Male to TNC Female** VSWR 1.2:1 to 6 GHz **Model No: PE91203**	 PRICE 1-24 $65.99 25-49 $62.69 50-99 $59.39 100+ $56.75 **TNC Male to TNC Female** VSWR 1.3:1 to 6 GHz **Model No: PE91240**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRECISION 1-24 $96.99 25-49 $92.14 50-99 $87.29 100+ $83.41 **TNC Male to TNC Female** VSWR 1.15:1 to 18 GHz **Model No:** PE91505	 Low PIM 1-24 $74.99 25-49 $71.24 50-99 $67.49 100+ $64.49 **TNC Male to TNC Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91173	 1-24 $31.39 25-49 $29.82 50-99 $28.25 100+ $27.00 **TNC Male to TNC Female** VSWR 1.5:1 to 11 GHz **Model No:** PE9270	 PRECISION 1-24 $165.99 25-49 $154.37 50-99 $142.75 100+ $132.79 **TNC Male to TNC Female** VSWR 1.15:1 to 18 GHz **Model No:** PE9443	 1-9 $211.99 10-24 $201.39 25-49 $190.79 50+ $182.31 **QD TNC Male to TNC Female** **Model No:** PE9561
2	 1-24 $43.79 25-49 $41.60 50-99 $39.41 100+ $37.66 **TNC Male to TNC Female** **Right Angle** Max. Freq. 11 GHz **Model No:** PE9100	 1-24 $127.99 25-49 $121.59 50-99 $115.19 100+ $110.07 **TNC Male to TNC Female** **Tee** **Model No:** PE9290	 1-24 $36.39 25-49 $34.57 50-99 $32.75 100+ $31.30 **TNC Female to TNC Male** **Tee** Max. Freq. 11 GHz **Model No:** PE9195	 1-24 $67.99 25-49 $64.59 50-99 $61.19 100+ $58.47 **TNC Female to TNC Female** VSWR 1.2:1 to 6 GHz **Model No:** PE91204	 1-24 $60.99 25-49 $57.94 50-99 $54.89 100+ $52.45 **TNC Female to TNC Female** VSWR 1.3:1 to 6 GHz **Model No:** PE91241
3	 1-24 $21.99 25-49 $20.89 50-99 $19.79 100+ $18.91 **TNC Female to TNC Female** VSWR 1.3:1 to 5 GHz **Model No:** PE9099	 Low PIM 1-24 $68.99 25-49 $65.54 50-99 $62.09 100+ $59.33 **TNC Female to TNC Female** VSWR 1.25:1 to 6 GHz **Model No:** PE91174	 1-24 $41.99 25-49 $39.89 50-99 $37.79 100+ $36.11 **TNC Female to TNC Female** **Tee** **Model No:** PE91381	 1-24 $55.99 25-49 $53.19 50-99 $50.39 100+ $48.15 **TNC Female to TNC Female** **Bulkhead** VSWR 1.35:1 to 12 GHz **Model No:** PE91430	 1-24 $48.19 25-49 $45.78 50-99 $43.37 100+ $41.44 **TNC Female to TNC Female** **Bulkhead** VSWR 1.3:1 to 6 GHz **Model No:** PE9154
4	 1-24 $41.59 25-49 $39.51 50-99 $37.43 100+ $35.77 **TNC Female to TNC Female** **4 Hole Flange** VSWR 1.3:1 to 11 GHz **Model No:** PE9288	 1-24 $66.99 25-49 $63.64 50-99 $60.29 100+ $57.61 **TNC Female to TNC Female** **Bulkhead** VSWR 1.2:1 to 6 GHz **Model No:** PE91205	 1-24 $81.99 25-49 $77.89 50-99 $73.79 100+ $70.51 **TNC Female to TNC Female** **Bulkhead** VSWR 1.3:1 to 6 GHz **Model No:** PE91242	 1-24 $39.39 25-49 $37.42 50-99 $35.45 100+ $33.88 **TNC Female to TNC Female** **Bulkhead** Max. Freq. 11 GHz **Model No:** PE9287	***TNC Between Series***
5	 PRECISION 1-4 $925.00 5-9 $878.75 10-24 $832.50 25+ $795.50 **TNC Male to 7mm Sexless** VSWR 1.15:1 to 18 GHz **Model No:** PE9219	 1-9 $317.99 10-24 $302.09 25-49 $286.19 50+ $273.47 **TNC Male to 7/16 DIN Female** VSWR 1.35:1 to 7.5 GHz **Model No:** PE9638	 1-24 $26.79 25-49 $25.45 50-99 $24.11 100+ $23.04 **TNC Male to BNC Female** VSWR 1.5:1 to 2 GHz **Model No:** PE9088	 1-24 $85.99 25-49 $81.69 50-99 $77.39 100+ $73.95 **TNC Male to BNC Female** **Right Angle** **Model No:** PE9783	 1-24 $145.99 25-49 $138.69 50-99 $131.39 100+ $125.55 **TNC Male to C Female** **Model No:** PE9562
6	 1-24 $26.59 25-49 $25.26 50-99 $23.93 100+ $22.87 **TNC Male to FME Plug** **Model No:** PE9699	 1-24 $15.79 25-49 $15.00 50-99 $14.21 100+ $13.58 **TNC Male to FME Plug** **Right Angle** **Model No:** PE9700	 1-24 $23.19 25-49 $22.03 50-99 $20.87 100+ $19.94 **TNC Male to FME Jack** **Model No:** PE9713	 1 Call - - - **TNC Male to HN Male** **Model No:** PE9563	 1-24 $89.99 25-49 $85.49 50-99 $80.99 100+ $77.39 **TNC Male to MCX Plug** **Model No:** PE9543
7	 1-24 $98.99 25-49 $94.04 50-99 $89.09 100+ $85.13 **TNC Male to MCX Jack** **Model No:** PE9542	 1-24 $29.19 25-49 $27.73 50-99 $26.27 100+ $25.10 **TNC Male to Mini UHF Female** **Model No:** PE9345	 1-24 $82.99 25-49 $78.84 50-99 $74.69 100+ $71.37 **TNC Male to SMC Jack** **Model No:** PE9226	 1-24 $35.39 25-49 $33.62 50-99 $31.85 100+ $30.44 **TNC Male to UHF Female** Max. Freq. 300 MHz **Model No:** PE9291	 PRECISION 1-9 $715.00 10-24 $679.25 25-49 $643.50 50+ $614.90 **TNC Female to 7mm Sexless** VSWR 1.15:1 to 18 GHz **Model No:** PE9218

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-9 $335.99 10-24 $319.19 25-49 $302.39 50+ $288.95 **TNC Female to 7/16 DIN Female** Max. Freq. 7.5 GHz **Model No: PE91392**	 PRICE 1-24 $37.19 25-49 $35.33 50-99 $33.47 100+ $31.98 **TNC Female to BNC Male** VSWR 1.3:1 to 4 GHz **Model No: PE9098**	 PRICE 1-24 $49.79 25-49 $47.30 50-99 $44.81 100+ $42.82 **TNC Female to BNC Female** VSWR 1.3:1 to 4 GHz **Model No: PE9097**	 PRICE 1-9 $169.99 10-24 $161.49 25-49 $152.99 50+ $146.19 **TNC Female to C Male** Max. Freq. 11 GHz **Model No: PE9564**	 PRICE 1-24 $7.18 25-49 $6.82 50-99 $6.46 100+ $6.17 **TNC Female to FME Jack** **Model No: PE9714**
2	 PRICE 1-24 $97.99 25-49 $93.09 50-99 $88.19 100+ $84.27 **TNC Female to MCX Plug** **Model No: PE9545**	 PRICE 1-24 $103.99 25-49 $98.79 50-99 $93.59 100+ $89.43 **TNC Female to MCX Jack** **Model No: PE9544**	 PRICE 1-24 $119.99 25-49 $113.99 50-99 $107.99 100+ $103.19 **TNC Female to MCX Jack Bulkhead-Mounting Hole B04** **Model No: PE9521**	 PRICE 1-24 $26.39 25-49 $25.07 50-99 $23.75 100+ $22.70 **TNC Female to Mini UHF Male** Max. Freq. 2.5 GHz **Model No: PE9346**	 PRICE 1-9 $265.99 10-24 $252.69 25-49 $239.39 50+ $228.75 **TNC Female to Limited Detent SMP Male Bulkhead** VSWR 1.3:1 to 8 GHz **Model No: PE91073**
3	 Low PIM PRICE 1-9 $57.99 10-24 $55.09 25-49 $53.35 50+ $51.61 **TNC Female to TNC Female** Max. Freq. 6 GHz **Model No: PE1279**	 PRICE 1-24 $46.19 25-49 $43.88 50-99 $41.57 100+ $39.72 **TNC Female to UHF Male** VSWR 1.3:1 to 300 MHz **Model No: PE9372**	***Reverse Polarity TNC In-Series*** →	 PRICE 1-24 $56.99 25-49 $54.14 50-99 $51.29 100+ $49.01 **TNC Male to Rev. Pol. TNC Female** **Model No: PE9532**	 PRICE 1-24 $46.19 25-49 $43.88 50-99 $41.57 100+ $39.72 **TNC Female to Rev. Pol. TNC Male** VSWR 1.32:1 to 6 GHz **Model No: PE9531**
4	 PRICE 1-24 $48.59 25-49 $46.16 50-99 $43.73 100+ $41.79 **Rev. Pol. TNC Male to Rev. Pol. TNC Female Right Angle** VSWR 1.25:1 to 6 GHz **Model No: PE9918**	***Reverse Polarity TNC Between Series*** →	 PRICE 1-24 $45.59 25-49 $43.31 50-99 $41.03 100+ $39.21 **Rev. Pol. TNC Female to BNC Male** Max. Freq. 4 GHz **Model No: PE91087**	***UHF In-Series*** →	 PRICE 1-24 $26.39 25-49 $25.07 50-99 $23.75 100+ $22.70 **UHF Male to UHF Male** VSWR 1.3:1 to 300 MHz **Model No: PE91487**
5	 PRICE 1-24 $42.79 25-49 $40.65 50-99 $38.51 100+ $36.80 **UHF Male to UHF Female Right Angle** VSWR 1.3:1 to 300 MHz **Model No: PE9209**	 PRICE 1-24 $32.99 25-49 $31.34 50-99 $29.69 100+ $28.37 **UHF Female to UHF Male Tee** **Model No: PE9095**	 PRICE 1-24 $60.99 25-49 $57.94 50-99 $54.89 100+ $52.45 **UHF Female to UHF Female Bulkhead-Mounting Hole F03** Max. Freq. 300 MHz **Model No: PE9114**	***UHF Between Series*** →	 PRICE 1-24 $35.79 25-49 $34.00 50-99 $32.21 100+ $30.78 **UHF Male to BNC Male** **Model No: PE9201**
6	 PRICE 1-24 $18.19 25-49 $17.28 50-99 $16.37 100+ $15.64 **UHF Male to BNC Female** VSWR 1.3:1 to 300 MHz **Model No: PE91328**	 PRICE 1-24 $46.99 25-49 $44.64 50-99 $42.29 100+ $40.41 **UHF Male to 75 Ohm F Female** **Model No: PE9165**	 PRICE 1-24 $25.79 25-49 $24.50 50-99 $23.21 100+ $22.18 **UHF Male to FME Plug** **Model No: PE9701**	 PRICE 1-24 $26.99 25-49 $25.64 50-99 $24.29 100+ $23.21 **UHF Male to Mini UHF Female** **Model No: PE9348**	 PRICE 1-24 $21.99 25-49 $20.89 50-99 $19.79 100+ $18.91 **UHF Female to BNC Male** VSWR 1.3:1 to 300 MHz **Model No: PE91329**
7	 PRICE 1-24 $32.99 25-49 $31.34 50-99 $29.69 100+ $28.37 **UHF Female to BNC Female** **Model No: PE9421**	 PRICE 1-24 $42.39 25-49 $40.27 50-99 $38.15 100+ $36.46 **UHF Female to 75 Ohm F Female** **Model No: PE9167**	 PRICE 1-24 $19.79 25-49 $18.80 50-99 $17.81 100+ $17.02 **UHF Female to Mini UHF Male** VSWR 1.3:1 to 300 MHz **Model No: PE91447**	***75 Ohm BNC In-Series*** →	 PRICE 1-24 $36.39 25-49 $34.57 50-99 $32.75 100+ $31.30 **75 Ohm BNC Male to 75 Ohm BNC Male** VSWR 1.5:1 to 300 MHz **Model No: PE9364**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $51.99 25-49 $49.39 50-99 $46.79 100+ $44.71 **75 Ohm BNC Male to 75 Ohm BNC Female** **Right Angle** Max. Freq. 4 GHz **Model No:** PE9361	 PRICE 1-24 $62.99 25-49 $59.84 50-99 $56.69 100+ $54.17 **75 Ohm BNC Female to 75 Ohm BNC Male** **Tee** Max. Freq. 100 MHz **Model No:** PE9365	 PRICE 1-24 $36.59 25-49 $34.76 50-99 $32.93 100+ $31.47 **75 Ohm BNC Female to 75 Ohm BNC Female** VSWR 1.3:1 to 1,000 MHz **Model No:** PE9362	 PRICE 1-24 $12.99 25-49 $12.34 50-99 $11.69 100+ $11.17 **75 Ohm BNC Female to 75 Ohm BNC Female** **Bulkhead** **Model No:** PEAD1266	 PRICE 1-24 $45.39 25-49 $43.12 50-99 $40.85 100+ $39.04 **75 Ohm BNC Female to 75 Ohm BNC Female** **Bulkhead** VSWR 1.3:1 to 1,000 MHz **Model No:** PE9363
2	 PRICE 1-24 $55.99 25-49 $53.19 50-99 $50.39 100+ $48.15 **75 Ohm BNC Female to 75 Ohm BNC Female 4 Hole Flange-Mounting Hole A03** Max. Freq. 1,000 MHz **Model No:** PE9367	 PRICE 1-24 $17.59 25-49 $16.71 50-99 $15.83 100+ $15.13 **75 Ohm BNC Female to 75 Ohm BNC Female** **Bulkhead** VSWR 1.5:1 to 500 MHz **Model No:** PE9791	***75 Ohm BNC Between Series***	 PRICE 1-24 $31.99 25-49 $30.39 50-99 $28.79 100+ $27.51 **75 Ohm BNC Female to 75 Ohm F Female** **Bulkhead** VSWR 1.3:1 to 1,000 MHz **Model No:** PE91324	***75 Ohm F In-Series***
3	 PRECISION PRICE 1-24 $52.99 25-49 $50.34 50-99 $47.69 100+ $45.57 **75 Ohm F Male to 75 Ohm F Male** VSWR 1.17:1 to 3 GHz **Model No:** PE91348	 PRICE 1-24 $129.99 25-49 $123.49 50-99 $116.99 100+ $111.79 **75 Ohm F Male to 75 Ohm F Male** VSWR 1.3:1 to 3 GHz **Model No:** PE9760	 PRICE 1-24 $12.39 25-49 $11.77 50-99 $11.15 100+ $10.66 **75 Ohm Push-On F Male to 75 Ohm F Female** VSWR 1.5:1 to 1,000 MHz **Model No:** PE9160	 PRICE 1-24 $129.99 25-49 $123.49 50-99 $116.99 100+ $111.79 **75 Ohm F Male to 75 Ohm F Female** VSWR 1.3:1 to 3 GHz **Model No:** PE9759	 PRECISION PRICE 1-24 $32.79 25-49 $31.15 50-99 $29.51 100+ $28.20 **75 Ohm F Female to 75 Ohm F Female** VSWR 1.28:1 to 3 GHz **Model No:** PE91349
4	 PRICE 1-24 $3.78 25-49 $3.59 50-99 $3.40 100+ $3.25 **75 Ohm F Female to 75 Ohm F Female** VSWR 1.35:1 to 500 MHz **Model No:** PE9164	 PRICE 1-24 $12.79 25-49 $12.15 50-99 $11.51 100+ $11.00 **75 Ohm F Female to 75 Ohm F Female** **Bulkhead** **Model No:** PEAD1265	 PRICE 1-24 $11.99 25-49 $11.39 50-99 $10.79 100+ $10.31 **75 Ohm F Female to 75 Ohm F Female** **Bulkhead-Mounting Hole B04** VSWR 1.3:1 to 250 MHz **Model No:** PE9734	***75 Ohm F Between Series***	 PRICE 1-9 $159.99 10-24 $151.99 25-49 $143.99 50+ $137.59 **75 Ohm F Male to 75 Ohm BNC Male** VSWR 1.3:1 to 3 GHz **Model No:** PE9742
5	 PRICE 1-9 $163.99 10-24 $155.79 25-49 $147.59 50+ $141.03 **75 Ohm F Male to 75 Ohm BNC Female** VSWR 1.3:1 to 3 GHz **Model No:** PE9743	 PRICE 1-24 $24.39 25-49 $23.17 50-99 $21.95 100+ $20.98 **75 Ohm F Male to 75 Ohm PAL Plug** **Model No:** PE9633	 PRICE 1-24 $24.39 25-49 $23.17 50-99 $21.95 100+ $20.98 **75 Ohm F Male to 75 Ohm PAL Jack** **Model No:** PE9632	 PRICE 1-9 $181.99 10-24 $172.89 25-49 $163.79 50+ $156.51 **75 Ohm F Female to 75 Ohm BNC Male** VSWR 1.3:1 to 3 GHz **Model No:** PE9741	 PRICE 1-9 $175.99 10-24 $167.19 25-49 $158.39 50+ $151.35 **75 Ohm F Female to 75 Ohm BNC Female** VSWR 1.3:1 to 3 GHz **Model No:** PE9744
6	 PRICE 1-24 $24.39 25-49 $23.17 50-99 $21.95 100+ $20.98 **75 Ohm F Female to 75 Ohm PAL Jack** **Model No:** PE9634	 PRICE 1-24 $23.79 25-49 $22.60 50-99 $21.41 100+ $20.46 **75 Ohm F Female to 75 Ohm RCA Plug** **Model No:** PE9163	***75 Ohm Mini SMB In-Series***	 PRICE 1-24 $47.79 25-49 $45.40 50-99 $43.01 100+ $41.10 **75 Ohm Mini SMB Plug to 75 Ohm Mini SMB Plug** **Model No:** PE9609	 PRICE 1-24 $67.99 25-49 $64.59 50-99 $61.19 100+ $58.47 **75 Ohm Mini SMB Plug to 75 Ohm Mini SMB Jack** **Model No:** PE9610
7	 PRICE 1-24 $47.79 25-49 $45.40 50-99 $43.01 100+ $41.10 **75 Ohm Mini SMB Jack to 75 Ohm Mini SMB Jack** **Model No:** PE9608	 PRICE 1-24 $61.99 25-49 $58.89 50-99 $55.79 100+ $53.31 **75 Ohm Mini SMB Jack to 75 Ohm Mini SMB Jack Bulkhead** **Model No:** PE9611	***75 Ohm Mini SMB Between Series***	 PRICE 1-24 $107.99 25-49 $102.59 50-99 $97.19 100+ $92.87 **75 Ohm Mini SMB Plug to 75 Ohm BNC Male** **Model No:** PE9616	 PRICE 1-24 $81.99 25-49 $77.89 50-99 $73.79 100+ $70.51 **75 Ohm Mini SMB Plug to 75 Ohm BNC Female** **Model No:** PE9617

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $103.99 25-49 $98.79 50-99 $93.59 100+ $89.43 **75 Ohm Mini SMB Jack to 75 Ohm BNC Male** **Model No:** PE9618	 PRICE 1-24 $117.99 25-49 $112.09 50-99 $106.19 100+ $101.47 **75 Ohm Mini SMB Jack to 75 Ohm BNC Female** **Model No:** PE9619	***75 Ohm N In-Series*** →	 PRICE 1-24 $47.99 25-49 $45.59 50-99 $43.19 100+ $41.27 **75 Ohm N Male to 75 Ohm N Male** Max. Freq. 1.5 GHz **Model No:** PE9308	 PRICE 1-24 $51.99 25-49 $49.39 50-99 $46.79 100+ $44.71 **75 Ohm N Male to 75 Ohm N Female** Max. Freq. 1.5 GHz **Model No:** PE9391
2	 PRICE 1-24 $60.99 25-49 $57.94 50-99 $54.89 100+ $52.45 **75 Ohm N Male to 75 Ohm N Female** **Right Angle** Max. Freq. 1.5 GHz **Model No:** PE9307	 PRICE 1-24 $45.79 25-49 $43.50 50-99 $41.21 100+ $39.38 **75 Ohm N Female to 75 Ohm N Female** VSWR 1.3:1 to 1,000 MHz **Model No:** PE9306	 PRICE 1-24 $143.99 25-49 $136.79 50-99 $129.59 100+ $123.83 **75 Ohm N Female to 75 Ohm N Female** **Bulkhead-Mounting Hole G01** **Model No:** PE9417	 PRICE 1-24 $76.99 25-49 $73.14 50-99 $69.29 100+ $66.21 **75 Ohm N Female to 75 Ohm N Female** **Bulkhead** VSWR 1.35:1 to 1.5 GHz **Model No:** PE9416	***75 Ohm N Between Series*** →
3	 PRICE 1-24 $89.99 25-49 $85.49 50-99 $80.99 100+ $77.39 **75 Ohm N Male to 75 Ohm BNC Male** Max. Freq. 1,000 MHz **Model No:** PE9370	 PRICE 1-24 $42.99 25-49 $40.84 50-99 $38.69 100+ $36.97 **75 Ohm N Male to 75 Ohm BNC Female** VSWR 1.3:1 to 1,000 MHz **Model No:** PE9369	 PRICE 1-9 $233.99 10-24 $222.29 25-49 $210.59 50+ $201.23 **75 Ohm N Male to 75 Ohm F Male** VSWR 1.3:1 to 3 GHz **Model No:** PE9738	 PRICE 1-24 $60.99 25-49 $57.94 50-99 $54.89 100+ $52.45 **75 Ohm N Male to 75 Ohm F Female** Max. Freq. 1,000 MHz **Model No:** PE9396	 PRICE 1-24 $127.99 25-49 $121.59 50-99 $115.19 100+ $110.07 **75 Ohm N Male to 75 Ohm Mini SMB Plug** **Model No:** PE9612
4	 PRICE 1-24 $109.99 25-49 $104.49 50-99 $98.99 100+ $94.59 **75 Ohm N Male to 75 Ohm Mini SMB Jack** **Model No:** PE9614	 PRICE 1-24 $139.99 25-49 $132.99 50-99 $125.99 100+ $120.39 **75 Ohm N Male to 75 Ohm SMB Plug** **Model No:** PE9584	 PRICE 1-24 $111.99 25-49 $106.39 50-99 $100.79 100+ $96.31 **75 Ohm N Male to 75 Ohm SMB Jack** **Model No:** PE9582	 PRICE 1-24 $113.99 25-49 $108.29 50-99 $102.59 100+ $98.03 **75 Ohm N Male to 75 Ohm SMC Jack** **Model No:** PE9586	 PRICE 1-24 $96.99 25-49 $92.14 50-99 $87.29 100+ $83.41 **75 Ohm N Male to 75 Ohm TNC Male** Max. Freq. 500 MHz **Model No:** PE9626
5	 PRICE 1-24 $67.99 25-49 $64.59 50-99 $61.19 100+ $58.47 **75 Ohm N Male to 75 Ohm TNC Female** Max. Freq. 500 MHz **Model No:** PE9627	 PRICE 1-24 $47.99 25-49 $45.59 50-99 $43.19 100+ $41.27 **75 Ohm N Female to 75 Ohm BNC Male** Max. Freq. 1,000 MHz **Model No:** PE9368	 PRICE 1-24 $62.99 25-49 $59.84 50-99 $56.69 100+ $54.17 **75 Ohm N Female to 75 Ohm BNC Female** Max. Freq. 1,000 MHz **Model No:** PE9371	 PRICE 1-24 $61.99 25-49 $58.89 50-99 $55.79 100+ $53.31 **75 Ohm N Female to 75 Ohm F Male** VSWR 1.3:1 to 3 GHz **Model No:** PE9397	 PRICE 1-24 $141.99 25-49 $134.89 50-99 $127.79 100+ $122.11 **75 Ohm N Female to 75 Ohm F Male** VSWR 1.3:1 to 3 GHz **Model No:** PE9739
6	 PRICE 1-9 $181.99 10-24 $172.89 25-49 $163.79 50+ $156.51 **75 Ohm N Female to 75 Ohm F Female** VSWR 1.3:1 to 3 GHz **Model No:** PE9740	 PRICE 1-9 $145.99 10-24 $138.69 25-49 $131.39 50+ $125.55 **75 Ohm N Female to 75 Ohm Mini SMB Plug** **Model No:** PE9613	 PRICE 1-24 $113.99 25-49 $108.29 50-99 $102.59 100+ $98.03 **75 Ohm N Female to 75 Ohm Mini SMB Jack** Max. Freq. 1,000 MHz **Model No:** PE9615	 PRICE 1-24 $149.99 25-49 $142.49 50-99 $134.99 100+ $128.99 **75 Ohm N Female to 75 Ohm SMB Plug** **Model No:** PE9585	 PRICE 1-24 $129.99 25-49 $123.49 50-99 $116.99 100+ $111.79 **75 Ohm N Female to 75 Ohm SMB Jack** **Model No:** PE9583
7	 PRICE 1-24 $121.99 25-49 $115.89 50-99 $109.79 100+ $104.91 **75 Ohm N Female to 75 Ohm SMC Plug** **Model No:** PE9589	 PRICE 1-24 $121.99 25-49 $115.89 50-99 $109.79 100+ $104.91 **75 Ohm N Female to 75 Ohm SMC Jack** **Model No:** PE9587	 PRICE 1-24 $67.99 25-49 $64.59 50-99 $61.19 100+ $58.47 **75 Ohm N Female to 75 Ohm TNC Male** Max. Freq. 500 MHz **Model No:** PE9628	 PRICE 1-24 $67.99 25-49 $64.59 50-99 $61.19 100+ $58.47 **75 Ohm N Female to 75 Ohm TNC Female** Max. Freq. 1,000 MHz **Model No:** PE9629	***75 Ohm PAL In-Series*** →

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $15.79 25-49 $15.00 50-99 $14.21 100+ $13.58 **75 Ohm PAL Plug to 75 Ohm PAL Plug** Model No: PE9680	***75 Ohm SMB In-Series*** →	 PRICE 1-24 $77.99 25-49 $74.09 50-99 $70.19 100+ $67.07 **75 Ohm SMB Plug to 75 Ohm SMB Plug** Model No: PE9271	 PRICE 1-24 $84.99 25-49 $80.74 50-99 $76.49 100+ $73.09 **75 Ohm SMB Jack to 75 Ohm SMB Plug Tee** Model No: PE9245	 PRICE 1-24 $84.99 25-49 $80.74 50-99 $76.49 100+ $73.09 **75 Ohm SMB Jack to 75 Ohm SMB Jack** Max. Freq. 4 GHz Model No: PE9248
2	***75 Ohm SMB Between Series*** →	 PRICE 1-24 $83.99 25-49 $79.79 50-99 $75.59 100+ $72.23 **75 Ohm SMB Plug to BNC Female** Model No: PE9232	 PRICE 1-24 $80.99 25-49 $76.94 50-99 $72.89 100+ $69.65 **75 Ohm SMB Plug to 75 Ohm Mini SMB Jack** Max. Freq. 2 GHz Model No: PE9736	 PRICE 1-24 $79.99 25-49 $75.99 50-99 $71.99 100+ $68.79 **75 Ohm SMB Jack to BNC Male** Model No: PE9229	 PRICE 1-24 $90.99 25-49 $86.44 50-99 $81.89 100+ $78.25 **75 Ohm SMB Jack to 75 Ohm Mini SMB Plug** Model No: PE9735
3	***75 Ohm SMC In-Series*** →	 PRICE 1-24 $71.99 25-49 $68.39 50-99 $64.79 100+ $61.91 **75 Ohm SMC Jack to 75 Ohm SMC Plug Tee** Model No: PE9244	 PRICE 1-24 $54.99 25-49 $52.24 50-99 $49.49 100+ $47.29 **75 Ohm SMC Jack to 75 Ohm SMC Jack** Model No: PE9227	 PRICE 1-24 $71.99 25-49 $68.39 50-99 $64.79 100+ $61.91 **75 Ohm SMC Jack to 75 Ohm SMC Jack Bulkhead-Mounting Hole B03** Model No: PE9228	***75 Ohm SMC Between Series*** →
4	 PRICE 1-24 $79.99 25-49 $75.99 50-99 $71.99 100+ $68.79 **75 Ohm SMC Jack to BNC Female** Model No: PE9235	***75 Ohm TNC In-Series*** →	 PRICE 1-24 $123.99 25-49 $117.79 50-99 $111.59 100+ $106.63 **75 Ohm TNC Male to 75 Ohm TNC Female Right Angle** Model No: PE9623	 PRICE 1-24 $48.99 25-49 $46.54 50-99 $44.09 100+ $42.13 **75 Ohm TNC Female to 75 Ohm TNC Female** Max. Freq. 1,000 MHz Model No: PE9622	 PRICE 1-24 $67.99 25-49 $64.59 50-99 $61.19 100+ $58.47 **75 Ohm TNC Female to 75 Ohm TNC Female Bulkhead-Mounting Hole B06** Max. Freq. 1,000 MHz Model No: PE9625
5	 PRICE 1-24 $115.99 25-49 $110.19 50-99 $104.39 100+ $99.75 **75 Ohm TNC Female to 75 Ohm TNC Female Bulkhead** Model No: PE9624	***75 Ohm TNC Between Series*** →	 PRICE 1-24 $36.79 25-49 $34.95 50-99 $33.11 100+ $31.64 **75 Ohm TNC Male to 75 Ohm BNC Female** Max. Freq. 500 MHz Model No: PE9631	 PRICE 1-24 $109.99 25-49 $104.49 50-99 $98.99 100+ $94.59 **75 Ohm TNC Male to 75 Ohm F Male** VSWR 1.35:1 to 2 GHz Model No: PE91081	 PRICE 1-24 $94.99 25-49 $90.24 50-99 $85.49 100+ $81.69 **75 Ohm TNC Male to 75 Ohm F Female** VSWR 1.35:1 to 2 GHz Model No: PE91080
6	 PRICE 1-24 $67.99 25-49 $64.59 50-99 $61.19 100+ $58.47 **75 Ohm TNC Female to 75 Ohm BNC Male** Max. Freq. 1,000 MHz Model No: PE9630	 PRICE 1-24 $121.99 25-49 $115.89 50-99 $109.79 100+ $104.91 **75 Ohm TNC Female to 75 Ohm F Male** VSWR 1.35:1 to 2 GHz Model No: PE91083	 PRICE 1-24 $103.99 25-49 $99.83 50-99 $96.71 100+ $94.63 **75 Ohm TNC Female to 75 Ohm F Female** VSWR 1.35:1 to 2 GHz Model No: PE91082	***BNC Twinax In-Series*** →	 PRICE 1-24 $109.99 25-49 $104.49 50-99 $98.99 100+ $94.59 **78 Ohm BNC Twinax Plug to 78 Ohm BNC Twinax Plug** Model No: PE9376
7	 PRICE 1-24 $107.99 25-49 $102.59 50-99 $97.19 100+ $92.87 **78 Ohm BNC Twinax Plug to 78 Ohm BNC Twinax Jack Right Angle** Model No: PE9377	 PRICE 1-24 $107.99 25-49 $102.59 50-99 $97.19 100+ $92.87 **78 Ohm BNC Twinax Jack to 78 Ohm BNC Twinax Plug Tee** Model No: PE9375	 PRICE 1-24 $48.79 25-49 $46.35 50-99 $43.91 100+ $41.96 **78 Ohm BNC Twinax Jack to 78 Ohm BNC Twinax Jack** Max. Freq. 500 MHz Model No: PE9378	 PRICE 1-24 $67.99 25-49 $64.59 50-99 $61.19 100+ $58.47 **78 Ohm BNC Twinax Jack to 78 Ohm BNC Twinax Jack Bulkhead** Max. Freq. 500 MHz Model No: PE9280	***3/4"-20 Twinax In-Series*** →

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 419 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $51.99 25-49 $49.39 50-99 $46.79 100+ $44.71 **95 Ohm 3/4"-20 Twinax Female to 95 Ohm 3/4"-20 Twinax Male Tee** Max. Freq. 400 MHz **Model No: PE9374**	 PRICE 1-24 $38.79 25-49 $36.85 50-99 $34.91 100+ $33.36 **95 Ohm 3/4"-20 Twinax Female to 95 Ohm 3/4"-20 Twinax Female** **Model No: PE9199**	 PRICE 1-24 $72.99 25-49 $69.34 50-99 $65.69 100+ $62.77 **95 Ohm 3/4"-20 Twinax Female to 95 Ohm 3/4"-20 Twinax Female Bulkhead** **Model No: PE9373**	***Banana Between Series*** →	 PRICE 1-24 $61.99 25-49 $58.89 50-99 $55.79 100+ $53.31 **Banana Plug to BNC Female** **Model No: PE9175**
2	***Double Banana Between Series*** →	 PRICE 1-24 $31.59 25-49 $30.01 50-99 $28.43 100+ $27.17 **Double Banana Plug to BNC Male** **Model No: PE9009**	 PRICE 1-24 $32.59 25-49 $30.96 50-99 $29.33 100+ $28.03 **Double Banana Plug to BNC Female** **Model No: PE9008**	***Banana Binding Post Between Series*** →	 PRICE 1-24 $24.99 25-49 $23.74 50-99 $22.49 100+ $21.49 **Banana Binding Post Jack to BNC Male** **Model No: PE9169**
3	***Double Banana Binding Post Between Series*** →	 PRICE 1-24 $36.39 25-49 $34.57 50-99 $32.75 100+ $31.30 **Double Banana Binding Post Jack to BNC Female** **Model No: PE9013**	***Non Constant Ohm BNC Triax In-Series*** →	 PRICE 1-9 $191.99 10-24 $182.39 25-49 $172.79 50+ $165.11 **BNC Triax Male to BNC Triax Female Tee** Max. Freq. 500 MHz **Model No: PE91106**	 PRICE 1-24 $54.99 25-49 $52.24 50-99 $49.49 100+ $47.29 **BNC Triax Female to BNC Triax Female** Max. Freq. 500 MHz **Model No: PE91107**
4	 PRICE 1-9 $185.99 10-24 $176.69 25-49 $167.39 50+ $159.95 **BNC Triax Female to BNC Triax Female Bulkhead-Mounting Hole B15** Max. Freq. 500 MHz **Model No: PE91105**	***Visit pasternack.com for our complete offering of adapters***			

See Our Website For Current Pricing & Real-Time Stock Availability!

Amplifiers Selection Guide

3 Easy Ways to Find your Product.....

1. Search by PE Part Number

If you know the PE part number you are searching for, please reference our Part Number Index on Page 404.

2. Quick Reference Guide

Bi Directional Amplifiers 52
Broadband Amplifiers 52
USB Controlled 54
Bench Top 54
DC Coupled Amplifiers 54
Gain Block Amplifiers 54
Limiting Amplifiers 55
Log Amplifiers 55
Low Noise Amplifiers 55
Standard 55
Input Protected 56
Temperature Compensated 57
Power Amplifiers 57
Power Amplifiers (<4W) 57
High Power Amplifiers (>4W) 59
GaN High Power Amplifiers 60
Variable Amplifiers 61
Amplifier Accessories 61

3. Amplifiers Locator

Frequency	Model No.	Page	C/R
DC to:			
1.5 GHz	PE15A86001	54	29
17 MHz	PE15A86002	54	28
2 GHz	PE15A86000	54	30
0.001 MHz to:			
1 GHz	PE15A63012	56	6
	PE15A63013	56	7
	PE15A63014	56	8
0.009 MHz to:			
3 GHz	PE15A1007	55	39
0.01 MHz to:			
1.4 GHz	PE15A1055	55	41
2 GHz	PE15A1059	55	42
3 GHz	PE15A3308	52	7
500 MHz	PE15A1046	55	40
0.03 MHz to:			
600 MHz	PE15A1047	55	43
0.1 MHz to:			
10 GHz	PE15A3311	52	8
0.15 MHz to:			
230 MHz	PE15A5028	59	18
	PE15A5028F	59	19
0.3 MHz to:			
6.5 GHz	PE15A3310	52	9
0.5 MHz to:			
500 MHz	PE15A5029	59	20
	PE15A5029F	59	21
1 MHz to:			
1 GHz	PE15A5030	57	42
	PE15A5030F	57	43
3 GHz	PE15A3309	52	10
500 MHz	PE15A1045	55	44
1.5 MHz to:			
100 MHz	PE15A5056	57	45

Frequency	Model No.	Page	C/R
1.5 MHz to:			
30 MHz	PE15A5055	57	44
10 MHz to:			
1 GHz	PE15A63000	56	9
	PE15A63001	56	10
	PE15A1011	55	50
	PE15A1049	55	51
	PE15A1012	55	52
	PE15A1013	55	53
	PE15A1052	55	54
1.3 GHz	PE15A1054	55	55
15 GHz	PE15A3037	54	97
20 GHz	PE15A4029	52	13
	PE15A3272	52	14
250 MHz	PE15A1043	55	45
3 GHz	PE1514	54	9
	PE1528	54	10
	PE1513	54	11
	PE15A1009	55	56
550 MHz	PE15A1044	55	46
6 GHz	PE15A4032	52	11
	PE15A3269	52	12
	PE15A8001	54	12
	PE15A63018	56	11
600 MHz	PE15A1063	55	47
800 MHz	PE15A1048	55	48
	PE15A1065	55	49
20 MHz to:			
1 GHz	PE15A1051	55	57
	PE15A1064	55	58
	PE15A5031	59	22
	PE15A5031F	59	23
	PE15A4072	57	47
	PE15A5057	57	48
1.5 GHz	PE15A1057	55	59

Frequency	Model No.	Page	C/R
20 MHz to:			
3 GHz	PE15A63016	56	12
	PE15A1008	55	60
	PE15A4017	57	49
4 GHz	PE15A1061	55	61
520 MHz	PE15A5065	57	46
30 MHz to:			
1.5 GHz	PE15A63002	56	13
	PE15A63003	56	14
2.5 GHz	PE15A5011	60	60
2.7 GHz	PE15B5003	52	1
	PE15A5086	57	50
20 GHz	PE15A3254	52	15
26.5 GHz	PE15A3312	52	16
3 GHz	PE15A63017	56	15
	PE15A4018	57	51
40 GHz	PE15A3023	52	17
40 MHz to:			
3 GHz	PE15A1060	55	62
50 MHz to:			
1 GHz	PE1517	54	13
	PE15A1050	55	63
	PE15A1014	55	64
	PE15A4009	57	52
1.2 GHz	PE15A1053	55	65
18 GHz	PE15A3900	54	95
2 GHz	PE1518	54	14
	PE15A1042	55	66
4 GHz	PE15A8000	54	15
40 GHz	PE15A3901	54	96
60 MHz to:			
6 GHz	PE15A4019	57	53
100 MHz to:			
12 GHz	PE15A3007	52	18

Frequency	Model No.	Page	C/R
100 MHz to:			
18 GHz	PE15A3255	52	19
	PE15A3256	52	20
	PE15A63020	56	16
	PE15A63015	56	17
	PE15A4052	57	54
	PE15A4052F	57	55
	PE15A7000	61	82
2 GHz	PE15A1066	55	67
26.5 GHz	PE15A3267	52	21
3 GHz	PE1516	54	16
6 GHz	PE15A5027	60	61
110 MHz to:			
10 GHz	PE15A3001	52	23
6 GHz	PE15A3004	52	22
200 MHz to:			
2.5 GHz	PE1525	54	17
2.6 GHz	PE15A5084	57	56
225 MHz to:			
512 MHz	PE15B5007	52	2
300 MHz to:			
18 GHz	PE15A3021	52	24
500 MHz to:			
1 GHz	PE15A5058	57	57
10 GHz	PE15A3005	52	30
18 GHz	PE15A3008	52	31
	PE15A3263	52	32
	PE15A2003	55	36
2 GHz	PE15A4038	52	25
	PE15A3014	52	26
	PE15A3015	52	27
	PE15A8004	54	18
	PE15A8005	54	19
	PE15A7001	61	83

Amplifiers Locator

Frequency	Model No.	Page	C/R
500 MHz to:			
2.5 GHz	PE15A4039	52	28
	PE15A5059	60	62
	PE15A5060	60	63
20 GHz	PE15A3253	52	33
3 GHz	PE15A1017	55	68
	PE15A1018	55	69
	PE15A5032	60	64
4 GHz	PE15A1068	55	70
	PE15A5101F	57	30
	PE15A5101	57	31
	PE15A4053	58	58
	PE15A4053F	58	59
	PE15A7002	61	84
6 GHz	PE15A4037	52	29
700 MHz to:			
2.2 GHz	PE15A5004	59	24
2.7 GHz	PE15A1067	55	71
	PE15A5033	60	65
	PE15A5033F	60	66
6 GHz	PE15A5017	60	67
800 MHz to:			
1 GHz	PE15A5061	58	60
2 GHz	PE15A5035F	59	27
	PE15A5077	58	61
	PE15A5078	58	62
2.5 GHz	PE15A5020	59	28
4.2 GHz	PE15A5062	60	68
	PE15A5034F	58	63
	PE15A5034	58	64
5.5 GHz	PE15A3264	52	34
960 MHz	PE15A5040	59	25
	PE15A5041	59	26
820 MHz to:			
960 MHz	PE15A4026	58	65
860 MHz to:			
960 MHz	PE15A5042	59	29
	PE15A5039	59	30
900 MHz to:			
1.2 GHz	PE15A63004	56	18
	PE15A63005	56	19
1 GHz to:			
1.4 GHz	PE15A63006	56	20
12 GHz	PE15A1031	56	75
18 GHz	PE15A3262	52	35
	PE15A7009	61	85
2 GHz	PE15A6002	55	31
	PE15A1000	55	72
	PE15A1019	55	73
	PE15A5063	60	69
	PE15A4025	58	66
	PE15A4016	58	67
2.5 GHz	PE15A5036F	59	31
	PE15A5036	59	32
	PE15A5082	59	33
	PE15A5081	59	34
	PE15A5085	58	68
	PE15A5083	58	69
20 GHz	PE15A3500	54	98
	PE15A3512	54	99
	PE15A3513	54	1
23 GHz	PE15A1074	56	22
26.5 GHz	PE15A7010	61	86
3 GHz	PE15A5026	60	70
	PE15A5037	60	35
	PE15A5037F	60	36
4 GHz	PE1519	54	20
	PE15A1070	55	74
40 GHz	PE15A3514	54	2
	PE15A3515	54	3
	PE15A3595	54	4
	PE15A7011	61	87
7 GHz	PE15A1075	56	21
1.2 GHz to:			
1.4 GHz	PE15A1023	56	76
	PE15A1024	56	77
	PE15A1005	56	78
	PE15A5001	60	37
1.6 GHz	PE15A1028	56	79
	PE15A5064	60	71
1.215 GHz to:			
1.4 GHz	PE15A1039	56	80
1.215 GHz to:			
1.4 GHz	PE15A1040	56	81
1.5 GHz to:			
3.5 GHz	PE15A5005	60	38
5 GHz	PE15A1034	56	82
1.7 GHz to:			
2.4 GHz	PE15A5073	60	39
2.5 GHz	PE15A5015	60	40
1.8 GHz to:			
4.2 GHz	PE15A3276	52	36
2 GHz to:			
12 GHz	PE15A4055	58	74
	PE15A4055F	58	75
18 GHz	PE15A5106	57	34
	PE15A5106F	57	35
	PE15A4051	53	47
	PE15A3301	53	48
	PE15A3257	53	49
	PE15A3258	53	50
	PE15A3265	53	51
	PE15A3022	53	52
	PE1524	54	23
	PE15A1030	56	87
	PE15A5068	60	76
	PE15A4056	58	76
	PE15A4056F	58	77
	PE15A4057	58	78
	PE15A4057F	58	79
2.6 GHz	PE15A63007	56	83
	PE15A5074	58	70
20 GHz	PE15A3271	53	53
	PE15A3270	53	54
	PE15A4027	53	55
	PE15A4030	53	56
	PE15A4058	58	80
	PE15A4058F	58	81
24 GHz	PE15A3009	53	57
35 GHz	PE15A3038	53	58
4 GHz	PE1520	54	21
	PE15A6015	55	32
	PE15A1001	56	84
	PE15A1041	56	85
	PE15A5038	60	41
4.4 GHz	PE15A4011	58	71
6 GHz	PE15A4040	52	37
	PE15A4041	52	38
	PE15A4003	52	39
	PE15A4005	52	40
	PE15A4042	52	41
	PE15A4043	52	42
	PE15A3503	52	43
	PE1521	54	22
	PE15A6007	55	33
	PE15A2001	55	37
	PE15A63019	56	23
	PE15A1010	56	86
	PE15A5066	60	72
	PE15A5067	60	73
	PE15A5024	60	74
	PE15A5025	60	75
	PE15A5047	60	42
	PE15A5047F	60	43
	PE15A7003	61	88
8 GHz	PE15A5104F	57	32
	PE15A5104	57	33
	PE15A3290	52	44
	PE15A3291	52	45
	PE15A3016	52	46
	PE15A6008	55	34
	PE15A4054	58	72
	PE15A4054F	58	73
	PE15A7004	61	89
2.3 GHz to:			
2.7 GHz	PE15A5018	60	44
2.4 GHz to:			
2.5 GHz	PE15B5000	52	3
2.5 GHz to:			
4 GHz	PE15A5006	60	45
2.6 GHz to:			
3.1 GHz	PE15A63008	56	24
	PE15A63009	56	25
4.2 GHz	PE15A5007	60	46
3 GHz to:			
8 GHz	PE15A1035	56	88
3.1 GHz to:			
3.5 GHz	PE15A4046	53	59
	PE15A63010	56	26
	PE15A63011	56	27
	PE15A1006	56	89
	PE15A5003	60	47
	PE15A5002	58	82
3.5 GHz to:			
7 GHz	PE15A5008	60	48
	PE15A4012	58	83
4 GHz to:			
12 GHz	PE15A5105	57	36
	PE15A5105F	57	37
	PE15A7005	61	90
8 GHz	PE1522	54	24
	PE15A1002	56	90
4.4 GHz to:			
4.9 GHz	PE15B5004	52	4
	PE15A5079	58	84
	PE15A5080	58	85
5.1 GHz	PE15B5005	52	5
5 GHz to:			
13 GHz	PE15A1073	57	28
9 GHz	PE15A9002	56	91
5.125 GHz to:			
5.875 GHz	PE15B5006	52	6
5.5 GHz to:			
9.5 GHz	PE15A5009	60	49
6 GHz to:			
10 GHz	PE15A5069	60	77
12 GHz	PE15A4044	53	60
	PE15A3292	53	61
	PE15A4045	53	62
	PE15A3293	53	63
	PE15A4001	53	64
	PE15A4004	53	65
	PE15A3506	53	66
	PE15A3505	53	67
	PE15A8006	54	25
	PE15A1032	56	92
	PE15A1072	56	93
	PE15A4060	58	86
	PE15A4060F	58	87
18 GHz	PE15A5107F	57	38
	PE15A5107	57	39
	PE15A3295	53	68
	PE15A3018	53	69
	PE15A3019	53	70
	PE15A3294	53	71
	PE15A3302	53	72
	PE15A3017	53	73
	PE15A3259	53	74
	PE15A3020	53	75
	PE15A8007	54	26
	PE1523	54	27
	PE15A6012	55	35
	PE15A2004	55	38
	PE15A1071	56	94
	PE15A5070	60	78
	PE15A5050	60	50
	PE15A5050F	60	51
	PE15A5049	60	52
	PE15A5049F	60	53
	PE15A4061F	58	88
	PE15A4061	58	89
	PE15A5048	58	90
	PE15A5048F	58	91
	PE15A4062	58	92
	PE15A4062F	58	93
	PE15A7006	61	91
6.4 GHz to:			
7.1 GHz	PE15A5016	61	79
7 GHz to:			
11 GHz	PE15A1033	56	95
17 GHz	PE15A3273	53	76
7.5 GHz to:			
11 GHz	PE15A4013	58	94
8 GHz to:			
11 GHz	PE15A4014	58	95
	PE15A4015	58	96
12 GHz	PE15A1027	56	96
	PE15A1026	56	97
	PE15A1003M	56	98
	PE15A1003	56	99
	PE15A1025	56	1
	PE15A5071	61	80
	PE15A5072	61	81
	PE15A5053	60	54
	PE15A5053F	60	55
	PE15A5052	60	56
	PE15A5051	58	97
	PE15A5051F	59	98
	PE15A4008	59	99
12.4 GHz	PE15A4063F	59	1
	PE15A4063	59	2
8.5 GHz to:			
10.5 GHz	PE15A5044	60	57
11 GHz	PE15A5043	60	58
	PE15A4006	59	3
	PE15A4007	59	4
12 GHz to:			
18 GHz	PE15A3296	53	77
	PE15A4002	53	78
	PE15A3507	53	79
	PE15A1004	56	2
12.4 GHz to:			
26.5 GHz	PE15A3024	53	80
14.4 GHz to:			
15.4 GHz	PE15A5021	59	5
17 GHz to:			
24 GHz	PE15A4028	53	81
27 GHz	PE15A3274	53	82
17.5 GHz to:			
21.5 GHz	PE15A4020	60	59
18 GHz to:			
26.5 GHz	PE15A3303	53	83
	PE15A3260	53	84
	PE15A4064	59	6
	PE15A4064F	59	7
	PE15A4021	59	8
	PE15A5054	59	9
	PE15A5054F	59	10
	PE15A7007	61	92
40 GHz	PE15A3268	53	85
	PE15A3025	53	86
	PE15A3304	53	87
	PE15A3305	53	88
	PE15A4065	59	11
	PE15A4065F	59	12
	PE15A7012	61	93
20 GHz to:			
40 GHz	PE15A3508	54	5
	PE15A3509	54	6
	PE15A3510	54	7
	PE15A3511	54	8
26.5 GHz to:			
40 GHz	PE15A5108F	57	40
	PE15A5108	57	41
	PE15A3261	53	89
	PE15A3266	53	90
	PE15A4022	53	91
	PE15A3306	53	92
	PE15A3307	53	93
	PE15A63021	57	29
	PE15A3300	56	3
	PE15A1076	56	4
	PE15A4050	59	13
	PE15A4067	59	14
	PE15A4067F	59	15
	PE15A7008	61	94
27 GHz to:			
40 GHz	PE15A1077	56	5
29 GHz to:			
36 GHz	PE15A3275	53	94
30 GHz to:			
40 GHz	PE15A4069	59	16
	PE15A4069F	59	17

BI-DIRECTIONAL AMPLIFIERS





Amplifier Type	Frequency Band (GHz.)	Tx Gain (dB)	Gain Var. ±(dB)	P1dB (W) Linear	Rx P1dB (dBm)	Rx NF (dB)	DC Power Tx (V/mA)	ECCN	Model No	1	2-4	5-9	10+	ROW
Bi Directional, High Power	30 MHz - 2.7	36	2			2	12/1,400	EAR99	PE15B5003	$8,480.00	$7,971.20	$7,547.20	$7,208.00	1
Bi Directional	225 MHz - 512 MHz		0.5			2.5	28/1,600	EAR99	PE15B5007	$15,550.00	$14,928.00	$14,306.00	$13,684.00	2
Bi Directional, High Power, High Rel	2.4 - 2.5	20		0.1	20		28/	EAR99	PE15B5000	$7,840.00	$7,526.40	$7,212.80	$6,899.20	3
Bi Directional	4.4 - 4.9	45	1			3.5	28/4,600	EAR99	PE15B5004	$20,700.00	$19,872.00	$19,044.00	$18,216.00	4
	4.4 - 5.1	10				3	28/1,750	EAR99	PE15B5005	$17,800.00	$17,088.00	$16,376.00	$15,664.00	5
	5.125 - 5.875	43	1.25				28/2,500	EAR99	PE15B5006	$17,725.00	$17,016.00	$16,307.00	$15,598.00	6

BROADBAND AMPLIFIERS







Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
Low Noise	0.01 MHz - 3	16	1.5	4	12		15/47	EAR99	PE15A3308	$875.00	See Web for Volume Pricing	7
	0.1 MHz - 10	33	6.5	5	13		12/110	EAR99	PE15A3311	$1,100.00		8
	0.3 MHz - 6.5	39	4.5	4	17		12/120	EAR99	PE15A3310	$1,060.00		9
	1 MHz - 3	21	1.5		22		15/110	EAR99	PE15A3309	$1,030.00		10
Low Noise		34	1	3	14.5		12/130	EAR99	PE15A3269	$740.00		12
Broadband, High Rel	10 MHz - 20	13	0.75		23	25	15/225	EAR99	PE15A4029	$5,950.00		13
Low Noise, High Rel		15	0.5		22	24	12/195	EAR99	PE15A3272	$6,270.00		14
	30 MHz - 20		2.5		20		15/180	EAR99	PE15A3254	$4,110.00		15
	30 MHz - 26.5		2	5.5	16		15/230	EAR99	PE15A3312	$3,810.00		16
Broadband	30 MHz - 40	25	2.5	6	20		11/400	EAR99	PE15A3023	$10,200.00		17
	100 MHz - 12	18	1	3	25	28	12/300	EAR99	PE15A3007	$2,960.00		18
Low Noise	100 MHz - 18	14	1.5		16	18	12/80	EAR99	PE15A3255	$1,630.00		19
		28	2.5				12/160	EAR99	PE15A3256	$3,330.00		20
Low Noise, High Rel	100 MHz - 26.5	15	2	5	15		15/200	EAR99	PE15A3267	$6,030.00		21
Broadband	110 MHz - 6	11	1.25	6.5	27	30	12/300	EAR99	PE15A3004	$2,840.00		22
	110 MHz - 10	10	1.5				12/300	EAR99	PE15A3001	$3,190.00		23
	300 MHz - 18	37	2		30.5		15/750	EAR99	PE15A3021	$6,550.00		24
Broadband, High Rel	500 MHz - 2	14	0.4	2.7	24		12/180	EAR99	PE15A4038	$1,200.00		25
		46	0.8				12/300	EAR99	PE15A3015	$1,600.00		27
	500 MHz - 2.5	24	0.5	3.5			12/240	EAR99	PE15A4039	$1,520.00		28
Broadband	500 MHz - 6				33	33	28/600	EAR99	PE15A4037	$5,100.00		29
	500 MHz - 10	32	1	3	25		12/375	EAR99	PE15A3005	$3,200.00		30
	500 MHz - 18	27	2.5				12/330	EAR99	PE15A3008	$3,760.00		31
Broadband, High Rel		33	1.5	4	15		12/220	EAR99	PE15A3263	$2,990.00		32
Low Noise, High Rel	500 MHz - 20	14	1.75	3	14		15/75	EAR99	PE15A3253	$3,260.00		33
Broadband, High Rel	800 MHz - 5.5	20	0.5		25	28	12/750	EAR99	PE15A3264	$1,830.00		34
	1 - 18	30	1.5		19	20	12/240	EAR99	PE15A3262	$3,430.00		35
Broadband, High Rel	2 - 6	13	0.4	5.4	23		12/180	EAR99	PE15A4040	$1,820.00		37
		22	0.6		27		12/420	EAR99	PE15A4041	$2,610.00		38
		32	1	5	33		15/1,700	EAR99	PE15A4003	$4,450.00		39
		33			30		12/1,000	EAR99	PE15A4005	$3,700.00		40
		36	1.5	6	34		15/2,200	EAR99	PE15A4042	$4,300.00		41
		44	1	4.5	35		12/4,200	EAR99	PE15A4043	$4,970.00		42
High Gain, High Rel				5	30		15/1,050	EAR99	PE15A3503	$3,580.00		43
Low Noise, High Rel	2 - 8	14		2.5	13		12/120	EAR99	PE15A3290	$2,000.00		44
		30					12/150	EAR99	PE15A3291	$2,520.00		45
Broadband, High Rel		33	1.5		29.4		8.5/941	EAR99	PE15A3016	$3,090.00		46

See Our Website For Current Pricing & Real-Time Stock Availability!

BROADBAND AMPLIFIERS







Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1	2-4	5-9	10+	ROW
Broadband	2 - 18	12	1.5		16		12/65	EAR99	PE15A4051	$1,900.00	$1,824.00	$1,748.00	$1,672.00	47
Low Noise		22	2.5	3.2	13		12/100	EAR99	PE15A3301	$6,250.00	$6,000.00	$5,750.00	$5,500.00	48
		26	2	3	14		12/150	EAR99	PE15A3257	$2,110.00	$2,025.60	$1,941.20	$1,856.80	49
		33	1				12/180	EAR99	PE15A3258	$2,600.00	$2,496.00	$2,392.00	$2,288.00	50
Broadband, High Rel			1.5	3.5	13		12/180	EAR99	PE15A3265	$2,950.00	$2,832.00	$2,714.00	$2,596.00	51
Broadband		37			30.5		15/800	EAR99	PE15A3022	$6,180.00	$5,932.80	$5,685.60	$5,438.40	52
		15		2.5	13	15.5	12/78	EAR99	PE15A3270	$5,180.00	$4,998.70	$4,817.40	$4,662.00	54
Broadband, High Rel							12/310	EAR99	PE15A4027	$6,970.00	$6,691.20	$6,412.40	$6,133.60	55
		31	0.75	3	26		15/400	EAR99	PE15A4030	$4,570.00	$4,387.20	$4,204.40	$4,021.60	56
Broadband	2 - 24	12		4		28	12/260	EAR99	PE15A3009	$2,470.00	$2,383.55	$2,297.10	$2,223.00	57
Broadband, High Rel	2 - 35		0.4		18	18.5	16/	3A001. B.4.C	PE15A3038	$8,360.00	$8,025.60	$7,691.20	$7,356.80	58
	3.1 - 3.5	30	0.7	4.5	30		12/900	EAR99	PE15A4046	$2,820.00	$2,707.20	$2,594.40	$2,481.60	59
	6 - 12	16	0.6	5	27		12/400	EAR99	PE15A4044	$2,600.00	$2,496.00	$2,392.00	$2,288.00	60
Low Noise, High Rel		17		2.5	7		12/100	EAR99	PE15A3292	$2,340.00	$2,246.40	$2,152.80	$2,059.20	61
Broadband, High Rel		28	0.8	5	27		12/500	EAR99	PE15A4045	$2,860.00	$2,745.60	$2,631.20	$2,516.80	62
Low Noise, High Rel		30		2.5			12/200	EAR99	PE15A3293	$2,690.00	$2,582.40	$2,474.80	$2,367.20	63
Broadband, High Rel		37	1.5	6	33		15/2,500	EAR99	PE15A4001	$4,290.00	$4,118.40	$3,946.80	$3,775.20	64
		38	1	5	30		15/1,300	EAR99	PE15A4004	$4,060.00	$3,897.60	$3,735.20	$3,572.80	65
High Gain, High Rel		47	1.5	6	33		15/2,500	EAR99	PE15A3506	$4,620.00	$4,435.20	$4,250.40	$4,065.60	66
		48	1	5	30		15/1,350	EAR99	PE15A3505	$3,890.00	$3,734.40	$3,578.80	$3,423.20	67
Low Noise, High Rel	6 - 18	14		3	13		12/100	EAR99	PE15A3295	$2,230.00	$2,140.80	$2,051.60	$1,962.40	68
Broadband, High Rel		30	1	3.5	28		12/1,300	EAR99	PE15A3018	$3,610.00	$3,465.60	$3,321.20	$3,176.80	69
			1.5		30		18/1,700	EAR99	PE15A3019	$4,590.00	$4,406.40	$4,222.80	$4,039.20	70
Low Noise, High Rel				2.5	10		12/200	EAR99	PE15A3294	$2,940.00	$2,822.40	$2,704.80	$2,587.20	71
Low Noise		32	1.5	2.3	14		12/150	EAR99	PE15A3302	$6,100.00	$5,856.00	$5,612.00	$5,368.00	72
Broadband, High Rel		36	2		27		15/800	EAR99	PE15A3017	$3,890.00	$3,734.40	$3,578.80	$3,423.20	73
Low Noise		38		2.5	22		12/280	EAR99	PE15A3259	$1,910.00	$1,833.60	$1,757.20	$1,680.80	74
Broadband, High Rel		33	2	6	30		15/2,000	EAR99	PE15A4002	$4,380.00	$4,204.80	$4,029.60	$3,854.40	78
High Gain, High Rel		43					15/2,000	EAR99	PE15A3507	$4,370.00	$4,195.20	$4,020.40	$3,845.60	79
Broadband	12.4 - 26.5	35		3	24.5		12/500	EAR99	PE15A3024	$8,830.00	$8,476.80	$8,123.60	$7,770.40	80
Broadband, High Rel	17 - 24	22			24		12/250	EAR99	PE15A4028	$4,330.00	$4,156.80	$3,983.60	$3,810.40	81
Low Noise, High Rel	17 - 27	19		2.75	13.5		12/96	EAR99	PE15A3274	$6,610.00	$6,345.60	$6,081.20	$5,816.80	82
Low Noise	18 - 26.5	32	2.5	2.3	11		12/250	EAR99	PE15A3303	$6,810.00	$6,537.60	$6,265.20	$5,992.80	83
		40	2	2.5	13		12/150	EAR99	PE15A3260	$2,530.00	$2,428.80	$2,327.60	$2,226.40	84
Low Noise, High Rel	18 - 40	18		5.5	10		15/250	3A001. B.4.C	PE15A3268	$8,830.00	$8,476.80	$8,123.60	$7,770.40	85
Broadband		30	2.5	6.5	20		12/350	EAR99	PE15A3025	$7,630.00	$7,324.80	$7,019.60	$6,714.40	86
Low Noise		32	2	4	12		12/200	EAR99	PE15A3304	$10,375.00	$9,960.00	$9,545.00	$9,130.00	87
		44	4		11		12/250	EAR99	PE15A3305	$11,450.00	$10,992.00	$10,534.00	$10,076.00	88
	26.5 - 40	22	1	3.5	13.5		12/125	EAR99	PE15A3261	$2,320.00	$2,227.20	$2,134.40	$2,041.60	89
		30	2	2	11		12/150	EAR99	PE15A3266	$6,650.00	$6,384.00	$6,118.00	$5,852.00	90
Broadband				6	20		12/350	EAR99	PE15A4022	$6,370.00	$6,115.20	$5,860.40	$5,605.60	91
Low Noise		35	2.5	2.4	10.5		12/150	EAR99	PE15A3306	$9,360.00	$8,985.60	$8,611.20	$8,236.80	92
		52	3.5	3.3	12		12/375	EAR99	PE15A3307	$11,350.00	$10,896.00	$10,442.00	$9,988.00	93
Low Noise, High Rel	29 - 36	20		2.9	11		3/80	EAR99	PE15A3275	$4,400.00	$4,224.00	$4,048.00	$3,872.00	94

See Our Website For Current Pricing & Real-Time Stock Availability!

USB CONTROLLED BROADBAND AMPS.



Amplifier Type	Frequency Band (GHz.)	Gain (dB)	NF (dB)	P1dB (dBm)	Control	ECCN	Model No	1	2-4	5-9	10+	ROW
USB	50 MHz - 18	12	4.5	10	USB	EAR99	PE15A3900	$3,750.00	$3,600.00	$3,450.00	$3,300.00	95
	50 MHz - 40		5			EAR99	PE15A3901	$7,380.00	$7,084.80	$6,789.60	$6,494.40	96

BENCH-TOP AMPLIFIERS





Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	DC Power (Optional DC In) (V)	AC Power (V/Cycle)	ECCN	Model No	1	2-4	5-9	10+	ROW
High Gain, High Rel	1 - 20	60	3	5	10		115/60	EAR99	PE15A3500	$14,550.00	$13,968.00	$13,386.00	$12,804.00	98
							220/	EAR99	PE15A3513	$13,950.00	$13,392.00	$12,834.00	$12,276.00	1
	1 - 40	40	2.5		22		120/60	EAR99	PE15A3595	$18,625.00	$17,973.13	$17,321.25	$16,762.50	4

GAIN BLOCK AMPLIFIERS







Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	IP3 (dBm)	DC Power (V/mA)	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
Gain Block	10 MHz - 3	12	10	5.5	10		15/40	EAR99	PE1514	$580.00	See Web for Volume Pricing	9
		15	2	3	11	12	18/40	EAR99	PE1528	$179.99		10
		20	14	2.7	13		15/50	EAR99	PE1513	$545.00		11
	10 MHz - 6	15	0.35	4.5	12	26	12/50	EAR99	PE15A8001	$840.00		12
	50 MHz - 1	22	0.75	3.5			12/150	EAR99	PE1517	$595.00		13
	50 MHz - 2		1				12/150	EAR99	PE1518	$740.00		14
	50 MHz - 4	26		5	22	35	12/120	EAR99	PE15A8000	$950.00		15
	100 MHz - 3	18	18	6	16		15/120	EAR99	PE1516	$630.00		16
	200 MHz - 2.5	22	1.25		15		15/120	EAR99	PE1525	$630.00		17
		50	1.8				12/180	EAR99	PE15A8005	$1,430.00		19
Gain Block	1 - 4	26	0.5	2.5	15		12/120	EAR99	PE1519	$1,170.00		20
	2 - 4	25					12/120	EAR99	PE1520	$1,210.00		21
	2 - 6	26		3			12/120	EAR99	PE1521	$1,150.00		22
	2 - 18	23	1	3.5	13		12/150	EAR99	PE1524	$1,470.00		23
	4 - 8	26	0.5	3	15		12/100	EAR99	PE1522	$1,260.00		24
Gain Block, High Rel	6 - 12	12	0.4	2.3	10	20	12/80	EAR99	PE15A8006	$1,600.00		25
	6 - 18	17	0.6	4.5	20		12/160	EAR99	PE15A8007	$2,230.00		26
Gain Block		22	1		13		12/150	EAR99	PE1523	$1,670.00		27

DC COUPLED AMPLIFIERS



Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	IP3 (dBm)	DC Power (V/mA)	ECCN	Model No	1-4	5-9	10-24	25+	ROW
DC Coupled	DC - 17 MHz	30			14		/45	EAR99	PE15A86002	$710.00	$674.50	$639.00	$610.60	28
	DC - 1.5	14			11	25	/45	EAR99	PE15A86001	$1,030.00	$978.50	$927.00	$885.80	29
	DC - 2	8		16			12/45	EAR99	PE15A86000	$990.00	$940.50	$891.00	$851.40	30

See Our Website For Current Pricing & Real-Time Stock Availability!

LIMITING AMPLIFIERS




Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	Input Power (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1	2-4	5-9	10+	ROW
Limitings, High Rel	1 - 2	60	3	3	-40 to 10	19	13/250	EAR99	PE15A6002	$2,750.00	$2,640.00	$2,530.00	$2,420.00	31
	2 - 6	80	3	4	-61 to 10	15	13/550	EAR99	PE15A6007	$3,520.00	$3,379.20	$3,238.40	$3,097.60	33
	2 - 8	40	2	5	-20 to 15	19	13/300	EAR99	PE15A6008	$2,710.00	$2,601.60	$2,493.20	$2,384.80	34
	6 - 18			4			13/300	EAR99	PE15A6012	$3,300.00	$3,168.00	$3,036.00	$2,904.00	35

LOG AMPLIFIERS




Amplifier Type	Frequency Band (GHz.)	Typ Recovery Time (ns)	Min TSS (dBm)	Log Linearity ± (dB)	Log Range (dBm)	Rise Time (ns)	Log Slope (mV/dB)	ECCN	Model No	1	2-4	5-9	10+	ROW
Log, High Rel	2 - 6	60	-73		-70 to 5	15	40	EAR99	PE15A2001	$12,725.00	$12,216.00	$11,707.00	$11,198.00	37
	6 - 18	150	-40	1	-40 to 0	20	50	EAR99	PE15A2004	$9,380.00	$9,004.80	$8,629.60	$8,254.40	38

LOW NOISE AMPLIFIERS

Standard






Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	IP3 (dBm)	DC Power (V/mA)	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
Low Noise	0.009 MHz - 3	32	1.25	2.5	16	29	15/110	EAR99	PE15A1007	$487.99	See Web for Volume Pricing	39
	0.01 MHz - 500 MHz	45	0.5		11	23	16/75	EAR99	PE15A1046	$835.00		40
	0.01 MHz - 1.4	42	1	3	19	32	16/120	EAR99	PE15A1055	$970.00		41
	0.01 MHz - 2	28	2	3.2	13	23	18/45	EAR99	PE15A1059	$700.00		42
	0.03 MHz - 600 MHz	50	1.2	2.2	14	24	18/85	EAR99	PE15A1047	$1,050.00		43
	1 MHz - 500 MHz	33.5	1.5	2	13		30/40	EAR99	PE15A1045	$700.00		44
	10 MHz - 250 MHz	17	0.5	1.4	22	39	5.25/160	EAR99	PE15A1043	$970.00		45
	10 MHz - 550 MHz	29.7	0.3	1.7	19	34	15/105	EAR99	PE15A1044	$880.00		46
	10 MHz - 600 MHz	40.5	0.8	0.9			15/140	EAR99	PE15A1063	$1,410.00		47
	10 MHz - 800 MHz	42	0.7	2	17	30	15/100	EAR99	PE15A1048	$835.00		48
		60	1.5	2.1		27	15/160	EAR99	PE15A1065	$1,610.00		49
High Gain	10 MHz - 1	30	0.7	1			15/110	EAR99	PE15A1011	$580.00		50
		32		2	12	23	15/40	EAR99	PE15A1049	$625.00		51
		40	1	0.8	17	31.5	15/110	EAR99	PE15A1012	$560.00		52
		50	1.25	1	18	28	15/140	EAR99	PE15A1013	$660.00		53
Low Noise		51	0.8	2.2	13	22	15/88	EAR99	PE15A1052	$955.00		54
	10 MHz - 1.3	35	0.5	1.5	20	34	15/165	EAR99	PE15A1054	$1,150.00		55
	10 MHz - 3	34	0.75	1.4	11	25	15/95	EAR99	PE15A1009	$875.00		56
	20 MHz - 1	30	0.5	1.3	18	32	18/140	EAR99	PE15A1051	$920.00		57
		30.5	0.8		19	34	15/140	EAR99	PE15A1064	$1,410.00		58
	20 MHz - 1.5	20	1.2	1	17	35	18/70	EAR99	PE15A1057	$835.00		59
	20 MHz - 3	25	0.75	1.6	13.5	25	15/75	EAR99	PE15A1008	$795.00		60
	20 MHz - 4		0.7	2	18	34	5.5/160	EAR99	PE15A1061	$1,190.00		61
	40 MHz - 3	16	1.6	1.3	7	22	3.3/18	EAR99	PE15A1060	$845.00		62
	50 MHz - 1	18	0.5	1	16	32	18/70	EAR99	PE15A1050	$790.00		63
		19			18	36	12/90	EAR99	PE15A1014	$373.99		64
	50 MHz - 1.2	47	1	2.2	13	23	15/88	EAR99	PE15A1053	$970.00		65
	50 MHz - 2	27	0.75	1.8	22	37	13.5/160	EAR99	PE15A1042	$800.00		66
	100 MHz - 2	61.5	1	2.5	19	33	15/170	EAR99	PE15A1066	$1,720.00		67
	500 MHz - 3	14.5	0.4	2	20	35	12/90	EAR99	PE15A1017	$409.99		68
		29	1	2.6		34	12/190	EAR99	PE15A1018	$520.00		69
	500 MHz - 4	24	2.5	0.7	17		15/65	EAR99	PE15A1068	$970.00		70
	700 MHz - 2.7	23			18	35	15/65	EAR99	PE15A1067	$970.00		71
Low Noise, High Rel	1 - 2	35	1	1.5	10		13/200	EAR99	PE15A1000	$1,690.00		72
High Gain		40		0.8	11	25	12/120	EAR99	PE15A1019	$1,230.00		73
Low Noise	1 - 4	20	1.2		20	41	15/120	EAR99	PE15A1070	$970.00		74

See Our Website For Current Pricing & Real-Time Stock Availability!

Standard






Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	IP3 (dBm)	DC Power (V/mA)	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
Low Noise, High Rel	1 - 12	16		1.75	17		6/60	EAR99	PE15A1031	$6,460.00		75
High Gain, High Rel	1.2 - 1.4	40	0.75	1.5	15		13.2/200	EAR99	PE15A1005	$1,370.00		78
Low Noise	1.2 - 1.6		0.5	0.8	12		15/100	EAR99	PE15A1028	$785.00		79
Integrated Band Pass Filter Low Noise	1.215 - 1.4	25	0.75	0.5	16		12/130	EAR99	PE15A1039	$1,180.00		80
		35					12/130	EAR99	PE15A1040	$1,090.00		81
Input Protected Low Noise	2 - 2.6	30	0.35	0.85	12		15/110	EAR99	PE15A63007	$1,130.00		83
Low Noise, High Rel	2 - 4	38	1	2	13		13/200	EAR99	PE15A1001	$1,840.00		84
Low Noise		40		0.7	14		15/100	EAR99	PE15A1041	$1,240.00		85
High Gain	2 - 6			0.9		25	15/110	EAR99	PE15A1010	$1,260.00		86
Low Phase Noise, High Rel	2 - 18	12.5		6.5	13		5/80	EAR99	PE15A1030	$11,725.00		87
	3 - 8	11		6	14	25	7/250	EAR99	PE15A1035	$7,050.00		88
High Gain, High Rel	3.1 - 3.5	40	0.3	1.1	15		17/150	EAR99	PE15A1006	$2,260.00		89
Low Noise, High Rel	4 - 8	38	1	2	13		13/250	EAR99	PE15A1002	$2,250.00		90
	5 - 9	22.5		1.75	14.8	25	12/105	EAR99	PE15A9002	$8,380.00		91
Low Phase Noise, High Rel	6 - 12	11	1	4.5	20	34	7/200	EAR99	PE15A1032	$7,430.00		92
Low Noise		25	0.7	2.1	11	25	5.5/65	EAR99	PE15A1072	$1,890.00		93
	6 - 18	26	2.5	1.9			5.5/65	EAR99	PE15A1071	$1,980.00		94
Low Phase Noise, High Rel	7 - 11	9		6	22	33	7/300	EAR99	PE15A1033	$8,340.00		95
Low Noise, High Rel	8 - 12	18	1	2.2	13		13/150	EAR99	PE15A1027	$1,960.00		96
		28					13/200	EAR99	PE15A1026	$2,400.00		97
		38					13/250	EAR99	PE15A1003M	$2,390.00		98
							13/250	EAR99	PE15A1003	$2,720.00		99
		48					13/300	EAR99	PE15A1025	$2,860.00		1
	12 - 18	38		3	13		13/300	EAR99	PE15A1004	$2,910.00		2
Low Noise	26.5 - 40	43	2	2	12	20	15/110	EAR99	PE15A3300	$3,960.00		3
Waveguide Low Noise		46	2.5	3	21	25	15/420	EAR99	PE15A1076	$11,400.00		4
	27 - 40	35	3		10	20	15/110	EAR99	PE15A1077	$10,525.00		5

Input Protected





Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	IP3 (dBm)	DC Power (V/mA)	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
Input Protected Low Noise	0.001 MHz - 1	40	1	1	15	27	15/80	EAR99	PE15A63012	$770.00		6
		50	1.25			30	15/110	EAR99	PE15A63013	$890.00		7
		60	1.5		16		15/130	EAR99	PE15A63014	$955.00		8
	10 MHz - 1	30	0.7		17	32	15/120	EAR99	PE15A63000	$830.00		9
		40	1			31.5	15/110	EAR99	PE15A63001	$825.00		10
	10 MHz - 6	30		3.5	14.5	37	15/100	EAR99	PE15A63018	$900.00		11
	20 MHz - 3	25	0.75	1.7	13	23	15/75	EAR99	PE15A63016	$925.00		12
	30 MHz - 1.5		0.5	1.6	22	39	15/150	EAR99	PE15A63002	$775.00		13
		29			23		15/160	EAR99	PE15A63003	$770.00		14
	30 MHz - 3	30		1.7	15	28	13/80	EAR99	PE15A63017	$955.00		15
	100 MHz - 18	33	1.5	3.5	21.5	30	15/280	EAR99	PE15A63020	$3,470.00		16
		38		3	17.5	26	15/300	EAR99	PE15A63015	$3,700.00		17
	900 MHz - 1.2	30	1	1.2	10		12/100	EAR99	PE15A63004	$780.00		18
		40					12/100	EAR99	PE15A63005	$720.00		19
	1 - 1.4	30					12/110	EAR99	PE15A63006	$720.00		20
GaN Input Protected Low Noise	1 - 7	42	3.5	1.5	22	31	28/200	EAR99	PE15A1075	$7,180.00		21
	1 - 23	29	1.5	3.5	20	32	28/250	EAR99	PE15A1074	$6,710.00		22
Input Protected Low Noise	2 - 6	40	1	1.2	14		15/90	EAR99	PE15A63019	$1,530.00		23
	2.6 - 3.1	30			10		12/120	EAR99	PE15A63008	$1,120.00		24
		40					12/120	EAR99	PE15A63009	$1,010.00		25
	3.1 - 3.5	28	0.5	0.8	8	20	15/45	EAR99	PE15A63010	$1,010.00		26
		35	1	0.85	13		12/100	EAR99	PE15A63011	$1,060.00		27

See Our Website For Current Pricing & Real-Time Stock Availability!

Input Protected



Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	IP3 (dBm)	DC Power (V/mA)	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
GaN Input Protected Low Noise	5 - 13	44	2.5	1.8	22	31	28/160	EAR99	PE15A1073	$7,600.00		See Web for Volume Pricing		28
Input Protected Low Noise	26.5 - 40	35	2	2.5	11	20	15/110	EAR99	PE15A63021	$3,890.00				29

Temperature Compensated Amplifiers





Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	DC Current (mA)	ECCN	Model No	1	2-4	5-9	10+	ROW
Low Noise	500 MHz - 4	39	1.75	3	21	350	EAR99	PE15A5101F	$6,710.00	$6,441.60	$6,173.20	$5,904.80	30
		47		4			EAR99	PE15A5101	$6,410.00	$6,153.60	$5,897.20	$5,640.80	31
	2 - 8	39	1.5	3.8	22		EAR99	PE15A5104F	$7,480.00	$7,180.80	$6,881.60	$6,582.40	32
		40		4.5			EAR99	PE15A5104	$7,190.00	$6,902.40	$6,614.80	$6,327.20	33
	2 - 18	39	2.5	5.5		550	EAR99	PE15A5106	$8,930.00	$8,572.80	$8,215.60	$7,858.40	34
							EAR99	PE15A5106F	$9,230.00	$8,860.80	$8,491.60	$8,122.40	35
	4 - 12	40	1.75	3.5		350	EAR99	PE15A5105	$8,930.00	$8,572.80	$8,215.60	$7,858.40	36
				4			EAR99	PE15A5105F	$9,230.00	$8,860.80	$8,491.60	$8,122.40	37
	6 - 18	43	2	4.7		400	EAR99	PE15A5107F	$8,240.00	$7,910.40	$7,580.80	$7,251.20	38
		47		4.5			EAR99	PE15A5107	$7,940.00	$7,622.40	$7,304.80	$6,987.20	39
	26.5 - 40	42	3	6.8	18		EAR99	PE15A5108F	$13,125.00	$12,600.00	$12,075.00	$11,550.00	40
		45		7			EAR99	PE15A5108	$12,825.00	$12,312.00	$11,799.00	$11,286.00	41

POWER AMPLIFIERS (<4W)






Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
High Power, Class AB	1 MHz - 1	36	1.5		33	36	28/1,200	EAR99	PE15A5030	$3,570.00		See Web for Volume Pricing		42
High Power, Class AB, Power with Fan							28/1,700	EAR99	PE15A5030F	$4,480.00				43
High Power, Class AB	1.5 MHz - 30 MHz	47	2			47	28/5,000	EAR99	PE15A5055	$6,090.00				44
High Power, Class AB	1.5 MHz - 100 MHz	47	2			47	28/5,000	EAR99	PE15A5056	$7,850.00				45
	20 MHz - 520 MHz	51				50	28/9,000	EAR99	PE15A5065	$7,370.00				46
Power	20 MHz - 1	40	0.5	6			24/630	EAR99	PE15A4072	$2,500.00				47
High Power, Class AB		49	2			49	28/11,000	EAR99	PE15A5057	$9,030.00				48
Power	20 MHz - 3	27	0.75		30		12/220	EAR99	PE15A4017	$980.00				49
High Power	30 MHz - 2.7	35	1.5			39	30/1,400	EAR99	PE15A5086	$13,450.00				50
Power	30 MHz - 3	38	1		30		12/270	EAR99	PE15A4018	$1,130.00				51
	50 MHz - 1	26	0.75	5	28		12/450	EAR99	PE15A4009	$1,600.00				52
	60 MHz - 6	36	1.5		29		15/530	EAR99	PE15A4019	$2,930.00				53
High Rel	100 MHz - 18	37	3	6	31		15/1,000	EAR99	PE15A4052	$13,400.00				54
High Rel, Power with Fan							15/2,160	EAR99	PE15A4052F	$13,025.00				55
Power, Class AB	200 MHz - 2.6	46	4		33	10	28/1,400	EAR99	PE15A5084	$12,650.00				56
High Power, Class AB	500 MHz - 1	50	2			50	28/10,000	EAR99	PE15A5058	$7,850.00				57

See Our Website For Current Pricing & Real-Time Stock Availability!

POWER AMPLIFIERS (<4W)







Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
High Rel	500 MHz - 4	30	3	6	30		12/1,500	EAR99	PE15A4053	$4,700.00		58
High Rel, Power with Fan							12/2,660	EAR99	PE15A4053F	$5,760.00		59
High Power, Class AB	800 MHz - 1	53	2			53	28/25,000	EAR99	PE15A5061	$7,850.00		60
Power, Class AB	800 MHz - 2	55	2.5		31	46	28/3,000	EAR99	PE15A5077	$13,250.00		61
Power, Class AB, Power with Fan		60	5		33		28/3,000	EAR99	PE15A5078	$14,700.00		62
Power, Class AB, Power with Fan	800 MHz - 4.2	31	2		30.8	31.8	13/1,000	EAR99	PE15A5034F	$3,600.00		63
Power, Class AB							13/800	EAR99	PE15A5034	$2,260.00		64
Power	820 MHz - 960 MHz	15	0.5	2	30		12/500	EAR99	PE15A4026	$635.00		65
High Power	1 - 2	35	0.75	1.5	36		12/800	EAR99	PE15A4016	$1,870.00		67
Power, Class AB	1 - 2.5	14	3			20	28/2,200	EAR99	PE15A5085	$10,775.00		68
		45	4		33	7	28/650	EAR99	PE15A5083	$11,925.00		69
	2 - 2.6	54	2.5		31	30	28/2,400	EAR99	PE15A5074	$11,400.00		70
High Power	2 - 4.4	32	0.5	10	36	37		EAR99	PE15A4011	$2,900.00		71
High Rel	2 - 8	38	2.5	5.5	30		12/1,200	EAR99	PE15A4054	$6,630.00		72
High Rel, Power with Fan							12/2,360	EAR99	PE15A4054F	$8,000.00		73
High Rel	2 - 12	35	4		33		15/4,500	EAR99	PE15A4055	$15,400.00		74
High Rel, Power with Fan							15/5,660	EAR99	PE15A4055F	$17,700.00		75
High Rel	2 - 18	30	2.5		30		12/2,500	EAR99	PE15A4056	$13,950.00		76
High Rel, Power with Fan							12/3,660	EAR99	PE15A4056F	$15,025.00		77
Power			4		33		12/5,000	EAR99	PE15A4057	$16,350.00		78
Power with Fan							12/6,160	EAR99	PE15A4057F	$17,350.00		79
High Rel	2 - 20		5.5		31		12/4,500	EAR99	PE15A4058	$16,775.00		80
High Rel, Power with Fan							12/5,660	EAR99	PE15A4058F	$16,575.00		81
High Power	3.1 - 3.5	45	1.5	4		40	15/5,000	EAR99	PE15A5002	$3,660.00		82
	3.5 - 7	26	2	11	36	37	/1,600	EAR99	PE15A4012	$3,590.00		83
Power, Class AB, Power with Fan	4.4 - 4.9	48	5		33	20	28/3,600	EAR99	PE15A5079	$17,675.00		84
							28/3,600	5A991.G	PE15A5080	$19,900.00		85
High Rel	6 - 12	47	2.5	6.5	30.5		12/1,500	EAR99	PE15A4060	$5,800.00		86
High Rel, Power with Fan							12/2,660	EAR99	PE15A4060F	$7,720.00		87
High Rel	6 - 18	30		7	27		12/1,380	EAR99	PE15A4061F	$7,640.00		88
							12/800	EAR99	PE15A4061	$6,760.00		89
High Rel, Power with Fan		35	3.5		33		12/2,500	EAR99	PE15A5048	$13,075.00		90
							12/3,660	EAR99	PE15A5048F	$14,175.00		91
High Rel		38		10	30		12/1,800	EAR99	PE15A4062	$11,625.00		92
High Rel, Power with Fan							12/2,960	EAR99	PE15A4062F	$12,800.00		93
High Power	7.5 - 11	25			33	37		EAR99	PE15A4013	$2,900.00		94
High Power	8 - 11	28	3		32	36		EAR99	PE15A4015	$2,480.00		96
High Rel	8 - 12	30	2		33		12/2,500	EAR99	PE15A5051	$7,970.00		97

See Web for Volume Pricing

See Our Website For Current Pricing & Real-Time Stock Availability!

POWER AMPLIFIERS (<4W)





Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1	2-4	5-9	10+	ROW
High Rel, Power with Fan	8 - 12	30	2		33		12/3,660	EAR99	PE15A5051F	$9,320.00	$8,947.20	$8,574.40	$8,201.60	98
Power		41	1	3.5	30	31	12/1,200	EAR99	PE15A4008	$4,150.00	$3,984.00	$3,818.00	$3,652.00	99
High Rel, Power with Fan	8 - 12.4	30	1.75	6	27		12/1,380	EAR99	PE15A4063F	$5,760.00	$5,529.60	$5,299.20	$5,068.80	1
High Rel							12/800	EAR99	PE15A4063	$4,940.00	$4,742.40	$4,544.80	$4,347.20	2
Power	8.5 - 11		0.5	3	30		15/900	EAR99	PE15A4006	$3,370.00	$3,235.20	$3,100.40	$2,965.60	3
			0.75	5	36		12/4,500	EAR99	PE15A4007	$4,620.00	$4,435.20	$4,250.40	$4,065.60	4
High Rel	18 - 26.5	28	2.5	7	27		12/1,150	EAR99	PE15A4064	$11,325.00	$10,872.00	$10,419.00	$9,966.00	6
High Rel, Power with Fan							12/1,730	EAR99	PE15A4064F	$11,950.00	$11,472.00	$10,994.00	$10,516.00	7
Power		33	1.25	5	31		12/1,800	EAR99	PE15A4021	$5,110.00	$4,905.60	$4,701.20	$4,496.80	8
High Rel		35	3		33		12/3,500	EAR99	PE15A5054	$15,175.00	$14,568.00	$13,961.00	$13,354.00	9
High Rel, Power with Fan							12/4,660	EAR99	PE15A5054F	$15,300.00	$14,688.00	$14,076.00	$13,464.00	10
High Rel	18 - 40		4	9	23		12/1,000	EAR99	PE15A4065	$13,425.00	$12,888.00	$12,351.00	$11,814.00	11
High Rel, Power with Fan							12/1,580	EAR99	PE15A4065F	$13,700.00	$13,152.00	$12,604.00	$12,056.00	12
Power	26.5 - 40		3	4.5	20	22	12/270	EAR99	PE15A4050	$3,710.00	$3,561.60	$3,413.20	$3,264.80	13
High Rel			4	10		27	12/3,000	EAR99	PE15A4067	$15,250.00	$14,716.25	$14,182.50	$13,725.00	14
High Rel, Power with Fan							12/3,160	EAR99	PE15A4067F	$16,525.00	$15,946.63	$15,368.25	$14,872.50	15
High Rel	30 - 40	20	2			20	12/350	EAR99	PE15A4069	$9,600.00	$9,216.00	$8,832.00	$8,448.00	16
High Rel, Power with Fan							12/930	EAR99	PE15A4069F	$10,300.00	$9,888.00	$9,476.00	$9,064.00	17

HIGH POWER AMPLIFIERS (>4W)





Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1	2-4	5-9	10+	ROW
High Power, Class AB	0.15 MHz - 230 MHz	43	1.5		41.8	44	28/5,000	EAR99	PE15A5028	$5,670.00	$5,443.20	$5,216.40	$4,989.60	18
							28/5,500	EAR99	PE15A5028F	$6,130.00	$5,884.80	$5,639.60	$5,394.40	19
High Power, Class AB, Power with Fan	0.5 MHz - 500 MHz	44			40	39	28/2,000	EAR99	PE15A5029	$2,990.00	$2,870.40	$2,750.80	$2,631.20	20
							28/2,000	EAR99	PE15A5029F	$3,190.00	$3,062.40	$2,934.80	$2,807.20	21
High Power, Class AB	20 MHz - 1	46				44	28/5,200	EAR99	PE15A5031	$4,720.00	$4,531.20	$4,342.40	$4,153.60	22
High Power, Class AB, Power with Fan							28/5,800	EAR99	PE15A5031F	$5,620.00	$5,395.20	$5,170.40	$4,945.60	23
High Power	700 MHz - 2.2	30	1	10	38	38.5		EAR99	PE15A5004	$2,870.00	$2,769.55	$2,669.10	$2,583.00	24
	800 MHz - 960 MHz			3			12/1,800	EAR99	PE15A5040	$1,620.00	$1,555.20	$1,490.40	$1,425.60	25
		37					12/1,800	EAR99	PE15A5041	$1,690.00	$1,622.40	$1,554.80	$1,487.20	26
High Power, Class AB	800 MHz - 2	41	1.5		40	40.8	13/5,500	EAR99	PE15A5035F	$5,800.00	$5,568.00	$5,336.00	$5,104.00	27
High Power, Class A	800 MHz - 2.5	40	2		41		12/5,500	EAR99	PE15A5020	$5,930.00	$5,692.80	$5,455.60	$5,218.40	28
High Power	860 MHz - 960 MHz	42	1	3.5		42.5	12/2,800	EAR99	PE15A5042	$3,440.00	$3,302.40	$3,164.80	$3,027.20	29
					44		12/6,500	EAR99	PE15A5039	$4,910.00	$4,713.60	$4,517.20	$4,320.80	30
High Power, Class AB, Power with Fan	1 - 2.5	40	1.5		39	40	13/5,500	EAR99	PE15A5036F	$6,290.00	$6,038.40	$5,786.80	$5,535.20	31
High Power, Class AB		44			41		13/5,000	EAR99	PE15A5036	$5,170.00	$4,963.20	$4,756.40	$4,549.60	32
Power, Class AB, Power with Fan		47	3		38	18	28/1,900	EAR99	PE15A5082	$14,650.00	$13,771.00	$13,038.50	$12,452.50	33
Power, Class AB		50					28/1,900	EAR99	PE15A5081	$12,475.00	$11,726.50	$11,102.75	$10,603.75	34

See Our Website For Current Pricing & Real-Time Stock Availability!

HIGH POWER AMPLIFIERS (>4W)





Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1	2-4	5-9	10+	ROW
High Power, Class AB	1 - 3	44	1.5		37.8	39	13/3,000	EAR99	PE15A5037	$6,380.00	$6,124.80	$5,869.60	$5,614.40	35
High Power, Class AB, Power with Fan							13/4,000	EAR99	PE15A5037F	$7,570.00	$7,267.20	$6,964.40	$6,661.60	36
High Power	1.2 - 1.4	40	0.3		40		12/4,000	EAR99	PE15A5001	$5,000.00	$4,800.00	$4,600.00	$4,400.00	37
	1.5 - 3.5	20	1.25	10	38.5	39		EAR99	PE15A5005	$3,050.00	$2,928.00	$2,806.00	$2,684.00	38
Power, Class AB	1.7 - 2.4	54	3		42	35	28/3,600	EAR99	PE15A5073	$10,850.00	$10,199.00	$9,656.50	$9,222.50	39
High Power	1.7 - 2.5	11	0.5		37		12/800	EAR99	PE15A5015	$3,060.00	$2,937.60	$2,815.20	$2,692.80	40
Power, Class AB	2 - 4	39	1.5		37.8	39	13/3,000	EAR99	PE15A5038	$6,600.00	$6,336.00	$6,072.00	$5,808.00	41
High Rel	2 - 6	40	3.5		37		12/7,000	EAR99	PE15A5047	$13,450.00	$12,912.00	$12,374.00	$11,836.00	42
High Rel, Power with Fan							12/8,160	EAR99	PE15A5047F	$14,725.00	$14,136.00	$13,547.00	$12,958.00	43
High Power	2.3 - 2.7	55	0.5		41.5		12/5,500	EAR99	PE15A5018	$7,030.00	$6,748.80	$6,467.60	$6,186.40	44
	2.5 - 4	19		8	38	38.5		EAR99	PE15A5006	$1,950.00	$1,872.00	$1,794.00	$1,716.00	45
	2.6 - 4.2		1	9	39	39		EAR99	PE15A5007	$2,020.00	$1,939.20	$1,858.40	$1,777.60	46
	3.1 - 3.5	47	1.5	3.5	43		12/9,000	EAR99	PE15A5003	$5,000.00	$4,800.00	$4,600.00	$4,400.00	47
	3.5 - 7	19	2	12	37	38		EAR99	PE15A5008	$4,040.00	$3,878.40	$3,716.80	$3,555.20	48
	5.5 - 9.5	24		8.5				EAR99	PE15A5009	$3,550.00	$3,408.00	$3,266.00	$3,124.00	49
High Rel	6 - 18	40	5		40		12/13,000	EAR99	PE15A5050	$23,250.00	$22,436.25	$21,622.50	$20,925.00	50
High Rel, Power with Fan							15/14,160	EAR99	PE15A5050F	$27,050.00	$26,103.25	$25,156.50	$24,345.00	51
High Rel		41			37		12/7,500	EAR99	PE15A5049	$20,450.00	$19,734.25	$19,018.50	$18,405.00	52
High Rel, Power with Fan							12/8,660	EAR99	PE15A5049F	$22,075.00	$21,302.38	$20,529.75	$19,867.50	53
High Rel	8 - 12	30	2.5		40		12/14,000	EAR99	PE15A5053	$20,275.00	$19,565.38	$18,855.75	$18,247.50	54
High Rel, Power with Fan							12/15,160	EAR99	PE15A5053F	$21,550.00	$20,795.75	$20,041.50	$19,395.00	55
High Rel		40	2		37		12/6,000	EAR99	PE15A5052	$15,025.00	$14,424.00	$13,823.00	$13,222.00	56
High Power	8.5 - 10.5	36	1.5		38.5		12/4,000	EAR99	PE15A5044	$5,580.00	$5,356.80	$5,133.60	$4,910.40	57
	8.5 - 11	30	0.75	5			12/7,500	EAR99	PE15A5043	$5,830.00	$5,596.80	$5,363.60	$5,130.40	58

GaN HIGH POWER AMPLIFIERS






Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1	2-4	5-9	10+	ROW
High Power	30 MHz - 2.5	43	2			40	28/1,200	EAR99	PE15A5011	$10,250.00	$9,840.00	$9,430.00	$9,020.00	60
	100 MHz - 6	60	1.25	10			28/2,200	EAR99	PE15A5027	$22,350.00	$21,456.00	$20,562.00	$19,668.00	61
High Power, Class AB	500 MHz - 2.5	48	2			47	28/7,000	EAR99	PE15A5059	$6,550.00	$6,157.00	$5,829.50	$5,567.50	62
		50			43	50	28/13,000	EAR99	PE15A5060	$15,000.00	$14,100.00	$13,350.00	$12,750.00	63
	500 MHz - 3	48			44	47	36/8,333	EAR99	PE15A5032	$18,500.00	$17,760.00	$17,020.00	$16,280.00	64
High Power, Class AB, Power with Fan	700 MHz - 2.7	45	1.5			50	30/8,733	EAR99	PE15A5033	$17,525.00	$16,824.00	$16,123.00	$15,422.00	65
							30/8,733	EAR99	PE15A5033F	$25,475.00	$24,583.38	$23,691.75	$22,927.50	66
High Power	700 MHz - 6	43	2			40	32/2,000	EAR99	PE15A5017	$11,525.00	$11,064.00	$10,603.00	$10,142.00	67
High Power, Class AB	800 MHz - 4.2	47				47	28/13,000	EAR99	PE15A5062	$10,225.00	$9,611.50	$9,100.25	$8,691.25	68
	1 - 2	53	1.5			53	28/20,000	EAR99	PE15A5063	$11,975.00	$11,256.50	$10,657.75	$10,178.75	69
High Power	1 - 3	50	1.25	10		47	28/4,000	EAR99	PE15A5026	$22,175.00	$21,288.00	$20,401.00	$19,514.00	70
High Power, Class AB	1.2 - 1.6	48	2.5				28/8,000	EAR99	PE15A5064	$5,590.00	$5,254.60	$4,975.10	$4,751.50	71
	2 - 6	43	2			43	28/3,000	EAR99	PE15A5066	$9,960.00	$9,362.40	$8,864.40	$8,466.00	72
		46				46	28/6,000	EAR99	PE15A5067	$16,325.00	$15,345.50	$14,529.25	$13,876.25	73
High Power, Class AB	2 - 18	37	3.5			37	22/2,500	EAR99	PE15A5068	$20,275.00	$19,058.50	$18,044.75	$17,233.75	76
	6 - 10	43	2			43	24/7,000	EAR99	PE15A5069	$19,000.00	$17,860.00	$16,910.00	$16,150.00	77
	6 - 18	40				40	28/3,000	EAR99	PE15A5070	$17,275.00	$16,238.50	$15,374.75	$14,683.75	78

See Our Website For Current Pricing & Real-Time Stock Availability!

GaN HIGH POWER AMPLIFIERS



Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1	2-4	5-9	10+	ROW
High Power	6.4 - 7.1	58				43	33/2,300	EAR99	PE15A5016	$11,575.00	$11,112.00	$10,649.00	$10,186.00	79
High Power, Class AB	8 - 12	43				43	28/5,000	EAR99	PE15A5071	$13,625.00	$12,807.50	$12,126.25	$11,581.25	80
		46				46	28/9,000	EAR99	PE15A5072	$21,800.00	$20,492.00	$19,402.00	$18,530.00	81

VARIABLE GAIN AMPLIFIERS





Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	Atten. Range (dB)	Step Size (dB)	AC Power (VAC)	ECCN	Model No	1	2-4	5-9	10+	ROW
Variable Gain, High Rel	100 MHz - 18	50	2	6.5	0-60	1	120	EAR99	PE15A7000	$21,325.00	$20,472.00	$19,619.00	$18,766.00	82
Variable Gain	500 MHz - 2	45	2	3.5				EAR99	PE15A7001	$8,340.00	$8,006.40	$7,672.80	$7,339.20	83
	500 MHz - 4	43		4				EAR99	PE15A7002	$9,740.00	$9,350.40	$8,960.80	$8,571.20	84
	1 - 18	48	3	3.5				EAR99	PE15A7009	$11,800.00	$11,328.00	$10,856.00	$10,384.00	85
	1 - 26.5	43	4	5.5				EAR99	PE15A7010	$15,875.00	$15,240.00	$14,605.00	$13,970.00	86
	1 - 40	45	5	5				EAR99	PE15A7011	$17,075.00	$16,392.00	$15,709.00	$15,026.00	87
	2 - 6	42	2	2				EAR99	PE15A7003	$9,740.00	$9,350.40	$8,960.80	$8,571.20	88
	2 - 8	43	3	2.5				EAR99	PE15A7004	$10,200.00	$9,792.00	$9,384.00	$8,976.00	89
	4 - 12	47		3.5				EAR99	PE15A7005	$9,680.00	$9,292.80	$8,905.60	$8,518.40	90
	6 - 18	45		3				EAR99	PE15A7006	$10,550.00	$10,128.00	$9,706.00	$9,284.00	91
	18 - 26.5			5.5				EAR99	PE15A7007	$13,225.00	$12,696.00	$12,167.00	$11,638.00	92
	18 - 40	48	5	5				EAR99	PE15A7012	$15,800.00	$15,168.00	$14,536.00	$13,904.00	93
	26.5 - 40	46	4					EAR99	PE15A7008	$14,550.00	$13,968.00	$13,386.00	$12,804.00	94

AMPLIFIER ACCESSORIES







Model No	Description	1 Pc. Price	See Web for Volume Pricing	ROW
PE15C5013	Heat Sink for Most RF Power Amplifier PE15A5000 Series	$545.00		95
PE15C5022	Heat Sink for Rf Power Amplifier PE15A5022	$735.00		96
PE15C5022F	Heat Sink with 24V Fan for RF Power Amplifier PE15A5022	$1,180.00		98
PE15C5014	Heatsink for amplifier models PE15A4011-4015 and PE15A5004-5009	$735.00		1
PE15G5060F	Heatsink for amplifier models PE15A5055-5059, PE15A5064-5065, PE15A5068 and PE15A5070	$855.00	See Web for Volume Pricing	2
PE15G5068F	Heatsink for amplifier models PE15A5060-5063, PE15A5066-5067, PE15A5069, PE15A5071-5072	$1,070.00		3
PE15J5011	Power and Control Cable for RF Amplifier PE15A5011, PE15A5014, PE15A5016, PE15A5017, PE15A5018, PE15A5019, PE15A5020 and PE15A5022	$279.99		4
PE15K5000	Power and Control Cable for RF Amplifier PE15B5000 and PE15B5001	$175.99		6
PE15J000	Power and Control Cable for RF Bi-Directional Amplifier PE15B5003	$397.99		8

See Our Website For Current Pricing & Real-Time Stock Availability!

INDEX GUIDE TO ANTENNAS

ANTENNAS..... 62

DIRECTIONAL ANTENNAS..... 62

Dish	63	Log	63
Fixed	60	Panel	62
Yagi	63	Sector	64

OMNI DIRECTIONAL ANTENNAS..... 64

Ceiling	64	Omni	67
Dome	65	Panel	67
Duplexed Antenna Kits	71	PCB	67
Fixed	62	Portable	68
GPS Active	66	Rubber Duck	66
GPS Passive	66	Vehicular	70
Mobile	66		

ANTENNA MOUNTS..... 71

Directional Antennas

Panel Antennas







RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
617 - 698 698 - 960 1,710 - 2,700 3,300 - 4,200 4,900 - 6,000	2:1	5.5 / 6 dBi	±45 Deg. Slant	PE51FP1012	$345.99	See Web for Volume Pricing	1
698 - 806 806 - 960 1,710 - 2,170 2,200 - 2,700 3,400 - 4,200	1.8:1	5 / 6 dBi	Vertical	PE51FP1013	$101.99		2
698 - 806 806 - 960 1,710 - 2,700 3,400 - 4,200	2:1		Vertical / Horizontal	PE51239	$285.99		3
			Vertical / Horizontal	PE51FP1014	$271.99		4
824 - 960	1.8:1	9 dBi	Vertical / Horizontal	PE51FP1006	$90.99		6
902 - 928	1.2:1	8.5 dBi	LHCP	PE51025	$195.99		7
			RHCP	PE51024	$211.99		8
	1.5:1	8 dBi	LHCP	PE51FP1007	$79.99		9
			RHCP	PE51FP1008	$79.99		10
			RHCP	PE51FP1008-1	$163.99		11
			RHCP	PE51FP1008-2	$163.99		12
			RHCP	PE51FP1008-3	$167.99		13
			Vertical / Horizontal	PE51FP1005	$94.99		14
			Vertical / Horizontal	PE51FP1005-1	$89.99		15
			Vertical / Horizontal	PE51FP1005-2	$89.99		16
			Vertical / Horizontal	PE51FP1005-3	$89.99		17
			Vertical / Horizontal	PE51FP1005-4	$89.99		18
	1.8:1	9 dBi	Vertical	PE51023	$343.99		19
2,400 - 2,500 4,900 - 5,850	2:1	11 dBi	Vertical / Horizontal	PE51FP1003	$315.99		20
		13 / 14 dBi	Vertical / Horizontal	PE51FP1004	$227.99		21
		9 / 10 dBi	Vertical / Horizontal	PE51FP1002	$229.99		22
		8 / 10 dBi	Vertical / Horizontal	PE51FP1001	$61.99		23
4,900 - 5,850 - 5,850	1.5:1	23 dBi	Vertical / Horizontal	PE51FP1010	$141.99		24
4,900 - 5,850	1.8:1	19 dBi	Vertical / Horizontal	PE51FP1011	$145.99		25

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Antennas



RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-4	5-9	10-24	25+	ROW
4,400 - 6,400	1.5:1	9 dBi	Vertical	PE51129	$655.00	$628.80	$609.15	$596.05	27

Yagi Antennas






RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
400 - 435 435 - 470	1.7:1	10 / 10.5 dBi	Linear	PE51YA1015	$169.99	$161.49	$152.99	$146.19	28
824 - 960	1.5:1	3 dBi	Vertical / Horizontal	PE51YA1007	$51.99	$49.39	$46.79	$44.71	29
		6 dBi	Vertical / Horizontal	PE51YA1008	$53.99	$51.29	$48.59	$46.43	30
		9 dBi	Vertical / Horizontal	PE51YA1009	$59.99	$56.99	$53.99	$51.59	31
		12 dBi	Vertical / Horizontal	PE51YA1010	$63.99	$60.79	$57.59	$55.03	32
		14 dBi	Vertical / Horizontal	PE51YA1011	$75.99	$72.19	$68.39	$65.35	33
880 - 928 928 - 960		11 / 11.5 dBi	Linear	PE51YA1017	$169.99	$161.49	$152.99	$146.19	34
		13 / 13 dBi	Linear	PE51YA1016	$183.99	$174.79	$165.59	$158.23	35
		7 / 7.5 dBi	Linear	PE51YA1019	$143.99	$136.79	$129.59	$123.83	36
		9 / 9.5 dBi	Linear	PE51YA1018	$163.99	$155.79	$147.59	$141.03	37
890 - 960		9 dBi	Vertical / Horizontal	PE51YA1012	$62.99	$59.84	$56.69	$54.17	38
		13 dBi	Vertical / Horizontal	PE51YA1013	$94.99	$90.24	$85.49	$81.69	39
900 - 928		14 dBi	Vertical / Horizontal	PE51YA1014	$205.99	$195.69	$185.39	$177.15	40
2,400 - 2,483		12 dBi	Vertical	PE51YA1004	$79.99	$75.99	$71.99	$68.79	41
2,400 - 2,500		9 dBi	Vertical / Horizontal	PE51YA1001	$85.99	$81.69	$77.39	$73.95	42
		12 dBi	Vertical / Horizontal	PE51YA1002	$94.99	$90.24	$85.49	$81.69	43
		14.5 dBi	Vertical / Horizontal	PE51YA1003	$93.99	$89.29	$84.59	$80.83	44
4,900 - 5,850		17 dBi	Vertical / Horizontal	PE51YA1006	$257.99	$245.09	$232.19	$221.87	45
5,725 - 5,825		16.5 dBi	Vertical	PE51YA1005	$119.99	$113.99	$107.99	$103.19	46

Dish Antennas



RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
2,400 - 2,500	1.5:1	18 dBi	H / V / 45 Deg. Slant	PE51PD1004	$199.99	$189.99	$179.99	$171.99	47
		22 dBi	H / V / 45 Deg. Slant	PE51PD1005	$237.99	$226.09	$214.19	$204.67	48
		25 dBi	H / V / 45 Deg. Slant	PE51PD1006	$429.99	$408.49	$386.99	$369.79	49
4,750 - 5,850 5,400 - 5,800		34	H / V / 45 Deg. Slant	PE51PD1003	$443.99	$421.79	$399.59	$381.83	50
		30 / 28	H / V / 45 Deg. Slant	PE51PD1002	$253.99	$241.29	$228.59	$218.43	51
4,750 - 5,850		25 dBi	H / V / 45 Deg. Slant	PE51PD1001	$215.99	$205.19	$194.39	$185.75	52

Log Antennas



RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
617 - 698 698 - 960 1,710 - 2,700	2 / 2 / 1.5:1	1 dBi	Vertical	PEANLP1003	$117.99	$112.09	$106.19	$101.47	53

See Our Website For Current Pricing & Real-Time Stock Availability!

Log Antennas






RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
698 - 960 1,710 - 2,500	1.6:1	9 / 10 dBi	Vertical / Horizontal	PE51LP1001	$107.99	$102.59	$97.19	$92.87	54
	2:1	10 / 11 dBi	Vertical	PEANLP1013	$95.99	$91.19	$86.39	$82.55	55
698 - 960 1,710 - 2,700			Vertical	PEANLP1014	$191.99	$182.39	$172.79	$165.11	56
			Vertical	PEANLP1015	$107.99	$102.59	$97.19	$92.87	57
			Vertical	PEANLP1012	$159.99	$151.99	$143.99	$137.59	58
790 - 960 1,710 - 2,170 2,300 - 2,700	1.7 / 1.5 / 1.5:1	10 dBi	Vertical / Horizontal	PEANLP1006	$53.99	$51.29	$48.59	$46.43	59
806 - 960 1,710 - 2,500	1.5:1	9 dBi	Vertical	PEANLP1007	$42.59	$40.46	$38.33	$36.63	60
806 - 960 1,710 - 2,700	2:1	9 / 10 dBi	Vertical	PEANLP1016	$77.99	$74.09	$70.19	$67.07	61
1,920 - 2,170	1.5:1	10 dBi	Vertical / Horizontal	PEANLP1008	$79.99	$75.99	$71.99	$68.79	62
2,300 - 2,500			Vertical / Horizontal	PEANLP1009	$79.99	$75.99	$71.99	$68.79	63
2,400 - 6,500		8 dBi	Vertical	PE51LP1002	$115.99	$110.19	$104.39	$99.75	64
3,400 - 3,600		14 dBi	Vertical	PEANLP1010	$79.99	$75.99	$71.99	$68.79	65
5,150 - 5,875	1.7:1	15 dBi	Vertical and Horizontal	PEANLP1005	$133.99	$127.29	$120.59	$115.23	66
5,725 - 5,850	1.5:1	16.5 dBi	Vertical	PEANLP1011	$53.99	$51.29	$48.59	$46.43	67

Sector Antennas





RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
698 - 960 1,710 - 2,700	1.6 / 1.7:1	14 / 14 dBi	Vertical	PE51SE1006	$455.99	$433.19	$410.39	$392.15	68
	1.8:1	12 / 12 dBi	Vertical	PE51SE1005	$437.99	$416.09	$394.19	$376.67	69
	1.9:1	10 / 10 dBi	45 Deg. Slant	PE51SE1004	$293.99	$279.29	$264.59	$252.83	70
900 - 930	2:1	13 dBi	Horizontal	PE51SE1003	$349.99	$332.49	$314.99	$300.99	71
902 - 960	1.5:1	12.5 dBi	Vertical / Horizontal	PE51FP1009	$505.00	$479.75	$454.50	$434.30	72
2,400 - 2,500	1.3:1	2 dBi	Vertical	PE51SE1009	$590.00	$560.50	$531.00	$507.40	73
	1.5:1	14 dBi	Vertical / Horizontal	PE51SE1001	$283.99	$269.79	$255.59	$244.23	74
2,400 - 2,500 4,900 - 5,850	1.5 / 2:1	13 / 15	Vertical / Horizontal	PE51SE1002	$550.00	$522.50	$495.00	$473.00	75
2,400 - 2,500 5,725 - 5,875	1.5:1	5 / 5 dBi	Vertical / Horizontal	PE51SE1007	$76.99	$73.14	$69.29	$66.21	76
4,900 - 5,850	1.7:1	16 dBi	Vertical / Horizontal	PE51SE1008	$165.99	$157.69	$149.39	$142.75	77

Omni Directional Antennas

Ceiling Antennas



RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
617 - 960 1,350 - 1,550 1,690 - 2,700 3,300 - 3,800 4,900 - 6,000 Mhz	1.8:1	1.5 / 3.5 dBi	Linear	PE51217	$115.99	$110.19	$104.39	$99.75	78
			Linear	PE51223	$121.99	$115.89	$109.79	$104.91	79
			Linear / Horizontal	PE51218	$211.99	$201.39	$190.79	$182.31	80
			Linear / Horizontal	PE51224	$221.99	$210.89	$199.79	$190.91	81

See Our Website For Current Pricing & Real-Time Stock Availability!

Ceiling Antennas





RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
617 - 698 698 - 960 1,710 - 2,700 3,400 - 4,200 4,900 - 6,000	1.8 / 1.8 / 1.5 / 1.7 / 1.7:1	1.8 / 2 dBi	vertical	PE51219	$115.99	$110.19	$104.39	$99.75	82
			vertical	PE51225	$119.99	$113.99	$107.99	$103.19	83
698 - 960 1,350 - 1,550 1,690 - 2,700 3,300 - 4,200	1.8:1	2.2 / 3.5 dBi	Linear	PE51220	$79.99	$75.99	$71.99	$68.79	84
			Linear	PE51226	$83.99	$79.79	$75.59	$72.23	85
698 - 806 806 - 960 1,350 - 1,550 1,710 - 2,700 3,300 - 4,200	1.8 / 1.8 / 2 / 1.8 / 1.8:1	1.5 / 2.2 dBi	Linear / Horizontal	PE51221	$105.99	$100.69	$95.39	$91.15	86
			Linear / Horizontal	PE51227	$111.99	$106.39	$100.79	$96.31	87
698 - 806 806 - 960 1,710 - 2,700 3,400 - 4,200	2:1	3 / 3.5 dBi	Vertical / Horizontal	PE51222	$107.99	$102.59	$97.19	$92.87	88
			Vertical / Horizontal	PE51228	$113.99	$108.29	$102.59	$98.03	89

Dome Antennas




RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
698 - 960 1,710 - 2,700	1.7 / 1.5:1	2 / 5 dBi	Vertical	PE51158	$43.79				90
800 - 3,000	2:1	3 dBi	Vertical	PE51059	$495.99		See Web for Volume Pricing		95
		7.5 dBi	Vertical	PE51058	$415.99				96
806 - 960 1,710 - 2,500	1.5:1	3 dBi	Vertical	PE51096	$58.99				97

Fixed Antennas



RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
902 - 928	2:1	5 dBi	Vertical	PE51028	$281.99				98
2,250 - 2,350	1.43:1	3 dB	Vertical	PE51062	$161.99				99
2,350 - 2,450	1.3:1	3 dBi	Vertical	PE51063	$349.99				1
2,400 - 2,500	2.1:1	8 dBi	Vertical	PE51172	$201.99		See Web for Volume Pricing		2
	2:1		Vertical	PE51061	$321.99				3
2,450 - 2,550	1.43:1	3 dB	Vertical	PE51064	$191.99				4
3,400 - 3,600	1.5:1	11 dBi	Vertical	PE51034	$127.99				5
3,450 - 3,550	1.4:1	3 dBi	Vertical	PE51065	$165.99				6
5,725 - 5,850	1.5:1	12 dBi	Vertical	PE51040	$143.99				8

See Our Website For Current Pricing & Real-Time Stock Availability!

GPS Active Antennas






RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
824 - 2,170	2.5:1	5 dBic	RHCP	PE51212	$15.99	See Web for Volume Pricing	9
1,166 - 1,606	1.8:1	43 dBi	RHCP	PE51GPS1005	$313.99		10
1,570 - 1,580	1.3:1	32 dBiC	RHCP	PE51067	$483.99		11
1,574 - 1,610	2:1	32 dBi	RHCP	PE51TM1000	$205.99		12
			RHCP	PE51TM1001	$245.99		13

GPS Passive Antennas




RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
1,220 - 1,230 1,530 - 1,580		6 dBic	RHCP	PE51068	$1,350.00	See Web for Volume Pricing	14
1,572.42 - 1,578.42	1.5:1	3 dBi	RHCP	PE51066-1	$165.99		15
			RHCP	PE51066-2	$127.99		16
1,575 - 1,615	2:1	3 dB	RHCP	PE51GPS1004	$37.79		17

Mobile Antennas






RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
824 - 960 1,710 - 2,200 2,400 - 2,500 Mhz	2:1	2 / 2 dBi	Vertical	PE51GM1002	$31.79	$29.56	$27.34	$25.43	18
880 - 965 1,710 - 2,170		3 dBi	Vertical	PE51113-1	$62.99	$59.84	$56.69	$54.17	19
			Vertical	PE51113-2	$69.99	$66.49	$62.99	$60.19	20
			Vertical	PE51113-3	$54.99	$52.24	$49.49	$47.29	21
			Vertical	PE51113-4	$57.99	$55.09	$52.19	$49.87	22
900 - 960 2,400 - 2,500	1.5:1		Vertical	PE51MO1001	$88.99	$84.54	$80.09	$76.53	23
		3 / 3 dBi	Vertical	PE51MO1002	$80.99	$76.94	$72.89	$69.65	24
		3 dBi	Vertical	PE51OM1022	$115.99	$110.19	$104.39	$99.75	25
902 - 928	2:1	4 dBi	Vertical	PE51027	$51.99	$49.39	$46.79	$44.71	26
2,400 - 2,500	1.5:1	3 dBi	Vertical	PE51MO1003	$113.99	$108.29	$102.59	$98.03	27
			Vertical	PE51OM1023	$109.99	$104.49	$98.99	$94.59	28
		5 dBi	Vertical	PE51MO1004	$83.99	$79.79	$75.59	$72.23	29
		3 dB	Vertical	PE51136	$141.99	$134.89	$127.79	$122.11	30

Omni Antennas






RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
617 - 960 1,710 - 2,700	2:1	6 / 6 dBi	Vertical	PE51OM1039	$305.99	See Web for Volume Pricing	31
617 - 960 1,710 - 3,800	2/2.5:1	7 / 7 dBi	Vertical	PE51OM1040	$243.99		32
698 - 960	2:1	6 dBi	Vertical	PE51OM1033	$233.99		33
			Vertical	PE51OM1034	$355.99		34
		8 dBi	Vertical	PE51OM1035	$307.99		35
			Vertical	PE51OM1036	$459.99		36
698 - 960	1.6:1	4 / 4 dBi	Vertical	PE51OM1020	$69.99		37
	1.7:1	6 / 8	Vertical	PE51OM1038	$273.99		38

See Our Website For Current Pricing & Real-Time Stock Availability!

Omni Antennas






RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
698 - 806 806 - 960 1,710 - 2,700 3,400 - 4,200	1.8:1	3 / 3 dBi	Vertical	PE51OM1031	$78.99	See Web for Volume Pricing	39
			Vertical	PE51OM1032	$82.99		40
824 -960	1.5:1	6 dBi	Vertical	PE51OM1014	$93.99		41
		3 / 6 dBi	Vertical	PE51OM1013	$84.99		42
		6 dBi	Vertical	PE51OM1015	$143.99		43
	1.6:1	8 dBi	Vertical	PE51OM1016	$207.99		44
			Vertical	PE51OM1019	$147.99		45
		3 / 6 dBi	Vertical	PE51OM1017	$88.99		46
		6 dBi	Vertical	PE51OM1018	$109.99		47
1,710 - 2,700	2.3:1	1 dBi	Vertical	PE51OM1043	$233.99		48
		6 dBi	Vertical	PE51OM1041	$207.99		49
		8 dBi	Vertical	PE51OM1042	$221.99		50
2,400 - 2,500	1.5:1	4 dBi	Vertical	PE51OM1024	$111.99		51
		12 dBi	Vertical / Horizontal	PE51OM1045	$273.99		52
	2:1	7.4 dBi	Vertical	PE51OM1025	$141.99		53
		8 dBi	Vertical	PE51OM1026	$105.99		54
2,400 - 2,500 5,100 - 5,800	1.6 / 1.8:1	6 / 11 dBi	Vertical / Horizontal	PE51OM1008	$417.99		55
		6 / 9 dBi	Vertical / Horizontal	PE51OM1007	$349.99		56
	1.6 / 1.9:1	6 dBi	Vertical / Horizontal	PE51OM1009	$287.99		57
		6 / 11 dBi	Vertical / Horizontal	PE51OM1011	$441.99		58
		6 / 6 dBi	Vertical / Horizontal	PE51OM1010	$355.99		59
2,400 - 2,500 5,725 - 5,850	1.5:1		Vertical	PE51OM1004	$153.99		60
	1.6:1	9 / 9 dBi	Vertical	PE51OM1005	$167.99		61
2,400 - 2,500 4,900 - 5,850	1.8:1	4 / 6 dBi	Vertical	PE51OM1012	$189.99		62
	2.5:1	5 / 6 dBi	Vertical	PE51OM1002	$67.99		63
		7 / 8 dBi	Vertical	PE51OM1003	$79.99		64
	2:1	3.5 / 4 dBi	Vertical	PE51OM1001	$58.99		65
2,400 - 2,500 5,100 - 5,900	1.6 / 1.8:1	6 / 6 dBi	Vertical / Horizontal	PE51OM1006	$279.99		66
2,500 - 2,700	1.5:1	12 dBi	Vertical	PE51OM1044	$193.99		67
3,300 - 3,800	2:1	1 dBi	Vertical	PE51OM1046	$165.99		68
		12 dBi	±45 Deg. Slant	PE51OM1049	$740.00		69
		13 dBi	±45 Deg. Slant	PE51OM1048	$491.99		70
		8 dBi	±45 Deg. Slant	PE51OM1047	$367.99		71

Panel Antennas



RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
617 - 698 698 - 960 1,710 - 2,700 3,300 - 4,200 4,900 - 6,000	2:1	5.5 / 6 dBi	±45 Deg. Slant	PE51FP1015	$361.99	$343.89	$325.79	$311.31	72
698 - 806 806 - 960 1,710 - 2,170 2,200 - 2,700 3,400 - 4,200	1.8:1	5 / 6 dBi	Vertical	PE51FP1016	$107.99	$102.59	$97.19	$92.87	73

PCB Antennas





RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
698 - 960 1,710 - 2,170 2,300 Mhz - 2,700	2.5:1	5 / 2.5 dBi	Vertical	PE51200	$7.69	$7.38	$7.15	$7.00	74

See Our Website For Current Pricing & Real-Time Stock Availability!

PCB Antennas





RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
704 - 960 1,574 - 1,576 1,710 - 2,200 2,496 - 2,690	2:1	3 dBi		PE51199	$8.69	$8.34	$8.08	$7.91	75
824 - 960	3:1	0 dBi	Vertical	PE51195	$11.19	$10.74	$10.41	$10.18	76
824 - 960 1,710 - 2,200	2.5:1			PE51198	$8.69	$8.34	$8.08	$7.91	77
	2:1	2 dBi		PE51197	$18.99	$18.23	$17.66	$17.28	78
824 - 960 1,710 - 1,880 1,900 - 2,200	3:1	0 dBi		PE51194	$11.19	$10.74	$10.41	$10.18	79
824 - 960 1,710 - 2,200		3 dBi	Vertical	PE51196	$11.19	$10.74	$10.41	$10.18	80
860 - 960		2 dBi	Vertical	PE51216	$16.39	$15.73	$15.24	$14.91	81
2,400 - 2,500	2.3:1		Vertical / Horizontal	PE51213	$16.59	$15.93	$15.43	$15.10	82
	2:1	1 dBi		PE51206	$6.59	$6.33	$6.13	$6.00	83
		2 dBi		PE51204	$5.18	$4.97	$4.82	$4.71	84
				PE51208	$6.59	$6.33	$6.13	$6.00	85
		2.6 dBi	Vertical	PE51209	$10.99	$10.55	$10.22	$10.00	86
		3 dBi		PE51205	$5.18	$4.97	$4.82	$4.71	87
				PE51207	$6.59	$6.33	$6.13	$6.00	88
		3.5 dBi	Vertical	PE51210	$10.99	$10.55	$10.22	$10.00	89
2,400 - 2,500 4,900 - 5,900	2.5:1	4.5 / 4.5 dBi	RHCP	PE51203	$8.29	$7.96	$7.71	$7.54	90
	2:1	2.5 dBi		PE51201	$7.99	$7.67	$7.43	$7.27	91
		3 dBi		PE51202	$8.29	$7.96	$7.71	$7.54	92
2,400 - 2,500 5,100 - 5,900		3 / 6 dBi	Vertical / Horizontal	PE51214	$21.19	$20.34	$19.71	$19.28	93
4,900 - 5,900		4.5 dBi	Horizontal	PE51215	$19.79	$19.00	$18.40	$18.01	94
5,150 - 5,850	2:1	3 dBi		PE51211	$5.49	$5.27	$5.11	$5.00	95

Portable Antennas







RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
118 - 174	2:1	0 dBi	Vertical	PE51TW1000	$39.39				96
400 - 420			Vertical	PE51146	$26.79				97
420 - 450			Vertical	PE51159	$31.99				98
470 - 512			Vertical	PE51161	$25.19				1
615 - 960 1,710 - 2,690	3:1	3 / 3 dBi	Vertical	PE51OM1030	$85.99				2
615 - 960 1,710 - 2,700		3.5 / 3.5 dBi	Vertical	PE51OM1027	$85.99				3
			Vertical	PE51OM1029	$85.99				4
615 - 960 1,400 - 2,700 3,300 - 4,200		4.5 / 4.5 dBi	Vertical	PE51RD1031	$25.99				5
615 - 960 1,710 - 2,700 3,300 - 4,200 5,150 - 7,150		3.5 / 2 dBi	Vertical	PE51RD1030	$36.19		See Web for Volume Pricing		6
617 - 960 1,710 - 2,690		3 / 3 dBi	Vertical	PE51OM1028	$85.99				7
617 - 960 1,427 - 2,700 3,300 - 5,850	3.5:1	2 / 2 dBi	Vertical	PE51RD1032	$30.99				8
698 - 780	2:1	0 dBi	Vertical	PE51157	$23.99				9
698 - 870	2.3:1	2 dBi	Vertical	PE51154	$31.59				10
	2:1		Vertical	PE51152	$26.39				11

See Our Website For Current Pricing & Real-Time Stock Availability!

Portable Antennas







RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
698 - 960 1,710 - 2,700	4.5 / 2:1	3 / 3 dBi	Vertical	PE51RD1027	$19.59		12
700 - 960 1,710 - 2,170 2,500 - 2,700	3 / 2.5 / 2.5:1	4 / 4 dBi	Vertical	PE51RD1028	$19.59		13
760 - 870	2:1	0 dBi	Vertical	PE51166	$29.79		14
824 - 928 900 - 928	1.7 / 1.5:1	8.5 / 10 dBi	Vertical / Horizontal	PE51OM1021	$930.00		15
880 - 960	2:1	0 dBi	Vertical	PE51164	$20.19		16
			Vertical	PE51165	$25.39		17
890 - 960 1,710 - 1,880		3 dBi	Vertical	PE51089-1	$54.99		18
			Vertical	PE51089-2	$47.39		19
			Vertical	PE51089-3	$44.99		20
			Vertical	PE51089-4	$45.19		21
900 - 960	1.5:1	0 dBi	Vertical	PE51056	$59.99		22
	2.1:1	3 dBi	Vertical	PE51055	$119.99		23
902 - 928	2:1		Vertical	PE51026	$30.59		24
1,700 - 1,850		3.5 dBi	Vertical	PE51119	$655.00		25
1,700 - 2,500		2 dBi	Vertical	PE51117A	$895.00		26
			Vertical	PE51173	$550.00		27
1,900 - 2,500		3.5 dBi	Vertical	PE51121	$850.00		28
2,200 - 2,500		6 dBi	Vertical	PE51123	$850.00		29
2,400 - 2,500	1.43:1	3 dBi	Vertical	PE51133	$229.99		30
	2:1	2.2 dBi	Vertical / Horizontal	PE51077	$45.99		31
		5.5 dBi	Vertical	PE51078	$27.79		32
2,400 - 2,500 4,900 - 5,800		2.5 dBi	Vertical	PE51087	$34.39		33
2,400 - 2,500 4,900 - 5,100 5,100 - 5,800	2 / 3 / 2.5:1	2 dBi	Vertical	PE51088	$45.19		34
2,400 - 2,500 4,900 - 5,825	2:1		Vertical	PE51080	$39.79		35
			Vertical	PE51082	$30.19		36
			Vertical	PE51083	$25.39		37
		2 / 3 dBi	Vertical	PE51081	$30.99		38
2,400 - 2,500 5,000 - 5,900		3.5 / 6 dBi	Vertical	PE51142	$36.19		39
			Vertical	PE51143	$23.79		40
2,400 - 7,125	1.7:1	3 dBi	Vertical	PE51RD1025	$29.59		42
			Vertical	PE51RD1026	$29.59		43
3,300 - 3,800	2:1	2 dBi	Vertical	PE51084	$44.59		44
3,400 - 3,800		5 dBi	Vertical	PE51085	$24.59		45
4,400 - 5,000		6 dBi	Vertical	PE51135A	$670.00		46
			Vertical	PE51134	$1,060.00		47
5,250 - 5,850		3.8 dBi	Vertical	PE51125A	$665.00		48
		6 dBi	Vertical	PE51127	$695.00		49

See Web for Volume Pricing

See Web for Volume Pricing

See Our Website For Current Pricing & Real-Time Stock Availability!

Rubber Duck Antennas





RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
860 - 960	2:1	3 dBi	Vertical	PE51RD1008	$27.99	$26.03	$24.07	$22.39	50
			Vertical	PE51RD1009	$27.99	$26.03	$24.07	$22.39	51
900 - 930	2.5:1	5 dBi	Vertical	PE51RD1019	$38.19	$35.52	$32.84	$30.55	52
			Vertical	PE51RD1010	$38.19	$35.52	$32.84	$30.55	53
			Vertical	PE51RD1011	$38.19	$35.52	$32.84	$30.55	54
			Vertical	PE51RD1012	$38.19	$35.52	$32.84	$30.55	55
	2:1		Linear	PE51RD1018	$23.39	$21.75	$20.12	$18.71	56
2,400 - 2,500		2 dBi	Linear	PE51RD1020	$11.79	$10.96	$10.14	$9.43	57
			Linear	PE51RD1022	$9.49	$8.83	$8.16	$7.59	58
			Linear	PE51RD1021	$5.49	$5.11	$4.72	$4.39	59
		3 dBi	Linear	PE51RD1013	$6.79	$6.31	$5.84	$5.43	60
			Linear	PE51RD1023	$6.79	$6.31	$5.84	$5.43	61
			Linear	PE51RD1024	$9.49	$8.83	$8.16	$7.59	62
		4.52 dBi	Linear	PE51RD1014	$18.59	$17.29	$15.99	$14.87	63
			Linear	PE51RD1015	$13.39	$12.45	$11.52	$10.71	64
			Linear	PE51RD1016	$18.59	$17.29	$15.99	$14.87	65
		5.5 dBi	Vertical	PE51RD1007	$18.19	$17.28	$16.37	$15.64	66
		7 dBi	Linear	PE51RD1017	$17.39	$16.17	$14.96	$13.91	67
2,400 - 2,500 4,900 - 5,850		3 / 3 dBi	Vertical	PE51RD1001	$25.39	$24.12	$22.85	$21.84	68
			Vertical	PE51RD1002	$24.79	$23.55	$22.31	$21.32	69
			Vertical	PE51RD1003	$25.39	$24.12	$22.85	$21.84	70
			Vertical	PE51RD1004	$24.99	$23.74	$22.49	$21.49	71
2,400 - 2,500 5,150 - 5,850		4.5 / 7 dBi	Vertical	PE51RD1006	$39.39	$37.42	$35.45	$33.88	72
2,400 - 2,483 5,100 - 5,900		3 / 5 dBi	Vertical	PE51RD1005	$31.39	$29.82	$28.25	$27.00	73

Vehicular Antennas





RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
108 - 520	2:1	2 dBi	Linear, Vertical	PE51MP1000	$68.99	$64.16	$59.33	$55.19	74
132 - 174	1.5:1	3 dB	Linear, Vertical	PE51MP1001	$83.99	$78.11	$72.23	$67.19	75
	2:1	2 dBi	Linear, Vertical	PE51MP1002	$91.99	$85.55	$79.11	$73.59	76
144 - 174	1.5:1	3 dB	Linear, Vertical	PE51MP1004	$83.99	$78.11	$72.23	$67.19	77
	2:1	2 dBi	Linear, Vertical	PE51MP1003	$121.99	$113.45	$104.91	$97.59	78
			Linear, Vertical	PE51MP1009	$91.99	$85.55	$79.11	$73.59	79
380 - 520			Linear, Vertical	PE51MP1005	$83.99	$78.11	$72.23	$67.19	80

See Our Website For Current Pricing & Real-Time Stock Availability!

Vehicular Antennas





RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
420 - 470	1.5:1	3 dB	Linear, Vertical	PE51MP1006	$77.99	$72.53	$67.07	$62.39	81
		5 dB	Linear, Vertical	PE51MP1007	$88.99	$82.76	$76.53	$71.19	82
440 - 480	2:1	3 dBd	Linear, Vertical	PE51MP1008	$94.99	$88.34	$81.69	$75.99	83
450 - 520 746 - 960		2 / 2 dBi	Linear, Vertical	PE51MP1011	$73.99	$68.81	$63.63	$59.19	84
698 - 960 1,710 - 2,150 2,150 - 2,700		2 / 3 dBi	Linear, Vertical	PE51MP1010	$67.99	$63.23	$58.47	$54.39	85
824 - 960 1,710 - 1,990		2 dBi	Vertical	PE51GM1001	$23.39	$21.75	$20.12	$18.71	86

Duplexed Antenna Kits Antennas




RF Frequency Range (MHz)	VSWR	Contains	Model No	1-24	25-49	50-99	100+	ROW
100 - 180 380 - 520 746 - 870	1.6:1	Duplexer (VHF/UHF 108-174 MHz/380-870 MHz), with integral N-type (m) Connectors (3 ea.); Low Loss 195 NMO mount with cable (1 ea.); RG-58/U NMO mount with cable (1 ea.); Field Tunable Antennas (2 ea.)//RG-58/U Feed Cable (1 ea.)	PE51AK1000	$309.99	$288.29	$266.59	$247.99	87
		Duplexer (VHF/UHF 108-174MHz/380-870MHz) with integral N-Type (m) Connectors (3 ea.); Low Loss PE51GPS1000 NMO Combination mount with integrated GPS antenna (1 ea.); RG-58/U NMO mount (1 ea.); Field Tunable Antennas (2 ea.); RG-58/U Feed Vable (1 ea.); PE51GPS1000 NMO Combination mount with integrated GPS antenna	PE51AK1001	$395.99	$368.27	$340.55	$316.79	88
		Duplexer (VHF/UHF 108-174MHz/450-520MHz/746-870MHz) with integral N-Type (m) Connectors (3 ea.); Low Loss PE51GPS1000 NMO Combination mount with integrated GPS antenna (1 ea.); RG-58/U NMO mount (1 ea.); PE51MP1011 multiband antenna (1 ea.); PE51MP1000 tunable VHF/UHF antenna (1 ea.)//RG-58/U Feed Cable (1 ea.)	PE51AK1002	$520.00	$483.60	$447.20	$416.00	89
		Duplexer (VHF/UHF 108-174MHz/450-520MHz/746-870MHz) with integral N-type (m) Connectors (3 ea.); Low loss 195 NMO mount (1 ea.); RG-58/U NMO mount (1 ea.); PE51MP1011 multiband antenna (1 ea.); PE51MP1000 tunable VHF/UHF antenna (1 ea.); RG-58/U Feed Cable (1 ea.)	PE51AK1003	$409.99	$381.29	$352.59	$327.99	90

Antenna Mounts




RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
800 - 900	1.2:1			PE51AK1004	$59.99	$55.79	$51.59	$47.99	91
1,575 - 1,615	2:1	3 dB	RHCP	PE51GPS1001	$181.99	$169.25	$156.51	$145.59	92
		28 dB	RHCP	PE51GPS1002	$159.99	$148.79	$137.59	$127.99	93
			RHCP	PE51GPS1003	$181.99	$169.25	$156.51	$145.59	94
1,575.42+/-3		3 dB	RHCP	PE51GPS1000	$159.99	$148.79	$137.59	$127.99	95

See Our Website For Current Pricing & Real-Time Stock Availability!

Attenuators and Equalizers Selection Guide

3 Easy Ways to Find your Product.....

1. Search by PE Part Number

If you know the PE part number you are searching for, please reference our Part Number Index on Page 404.

2. Quick Reference Guide

Attenuators..... 72
- **CMOS, Relay, TTL and USB Controlled Attenuators..... 90**
- **Continuously Variable Attenuators**
  - 50 Ohm..... 90
- **DC Bias Attenuators**
  - 50 Ohm..... 89
  - 75 Ohm..... 90
- **Fixed Attenuators**
  - 50 Ohm..... 74
  - 75 Ohm..... 87
- **Step Attenuators, Push Button**
  - 50 Ohm..... 88
  - 75 Ohm..... 88
- **Step Attenuators, Rotary**
  - 50 Ohm..... 89
  - 75 Ohm..... 89
- **Step Attenuators, Toggle**
  - 75 Ohm..... 88
- **Voltage Variable Attenuators..... 90**

Equalizers..... 91

3. Attenuators Locator

Connector In-Out	Max Freq.	Power	Model No.	Page
1.85mm Male				
1.85mm Female	65 GHz	1 W	PE7403	74
2.4mm Female				
2.4mm Female	40 GHz	0.25 W	PE70A6001	91
2.4mm Male				
2.4mm Female	50 GHz	1 W	PE7089	74
2.92mm Female				
2.92mm Female	18 GHz	0.25 W	PE70A5001	91
	40 GHz	0 W	PE70A8008	91
	40 GHz	0.2 W	PE70A3901	91
	40 GHz	0.25 W	PE70A5002	91
2.92mm Male				
2.92mm Female	26.5 GHz	2 W	PE7024	75
	40 GHz	0.5 W	PE7429	74
	40 GHz	1 W	PE7088	74
	40 GHz	2 W	PE7430	75
	40 GHz	10 W	PE7AP4009	79
4.3-10 Male				
4.3-10 Female	6 GHz	15 W	PE7AP1001	80
7/16 DIN Female				
7/16 DIN Female	6 GHz	25 W	PE7380	81
	6 GHz	50 W	PE7313	82
	6 GHz	100 W	PE7204	84
	7.5 GHz	25 W	PE7380	81
	7.5 GHz	50 W	PE7313	82
7/16 DIN Male	6 GHz	50 W	PE7310	82
	6 GHz	100 W	PE7201	84
	7.5 GHz	50 W	PE7310	82

Connector In-Out	Max Freq.	Power	Model No.	Page
7/16 DIN Female				
N Female	6 GHz	50 W	PE7316	82
	6 GHz	100 W	PE7212	84
	7.5 GHz	50 W	PE7316	82
	18 GHz	50 W	PE7321	82
N Male	6 GHz	100 W	PE7207	84
7/16 DIN Male				
7/16 DIN Female	6 GHz	25 W	PE7379	81
	6 GHz	50 W	PE7312	82
	6 GHz	100 W	PE7203	84
	7.5 GHz	5 W	PE7039	79
	7.5 GHz	10 W	PE7040	80
	7.5 GHz	25 W	PE7379	81
	7.5 GHz	50 W	PE7312	82
N Female	6 GHz	100 W	PE7211	84
BNC Female				
BNC Female	0.5 GHz	1 W	PE7008	88
	0.5 GHz	1 W	PE7035	89
	0.75 GHz	1 W	PE7008	88
	1 GHz	1 W	PE70A1001	88
	1 GHz	1 W	PE7034	89
	1 GHz	1 W	PE7035	89
	2 GHz	2 W	PE7034	89
	2.2 GHz	2 W	PE70A1024	89
BNC Male				
BNC Female	1 GHz	1 W	PE7009	87
	1 GHz	100 W	PE7026	85
	2 GHz	1 W	PE7000	75

Attenuators Locator

Connector In-Out	Max Freq.	Power	Model No.	Page
BNC Male				
BNC Female	2 GHz	10 W	PE7025	80
	4 GHz	2 W	PE7049	76
	4 GHz	2 W	PE7050	87
F Female				
F Female	1 GHz	1 W	PE70A1008	88
	1 GHz	1 W	PE70A8003	90
	2.15 GHz	0.01 W	PE70A5012	91
	2.15 GHz	0.1 W	PE70A5011	91
F Male				
F Female	1 GHz	2 W	PE7057	87
	2 GHz	2 W	PE7064	90
	3 GHz	2 W	PE7396	87
N Female				
7/16 DIN Female	6 GHz	25 W	PE7369	81
	6 GHz	50 W	PE7315	83
	6 GHz	100 W	PE7206	85
	7.5 GHz	25 W	PE7369	81
	7.5 GHz	50 W	PE7315	83
7/16 DIN Male	6 GHz	25 W	PE7370	81
	6 GHz	50 W	PE7311	83
	6 GHz	100 W	PE7202	85
	7.5 GHz	25 W	PE7370	81
	7.5 GHz	50 W	PE7311	83
N Female	6 GHz	50 W	PE7323	83
	6 GHz	100 W	PE7214	85
	8 GHz	25 W	PE7371	81
	18 GHz	25 W	PE7371	81
	18 GHz	50 W	PE7323	83
N Male	6 GHz	50 W	PE7317	83
	6 GHz	100 W	PE7208	85
	18 GHz	50 W	PE7317	83
TNC Female	18 GHz	25 W	PE7372	81
N Male				
7/16 DIN Female	6 GHz	25 W	PE7366	81
	6 GHz	50 W	PE7314	83
	6 GHz	100 W	PE7205	85
	7.5 GHz	25 W	PE7366	81
	7.5 GHz	50 W	PE7314	83
N Female	1 GHz	1 W	PE7029	87
	1 GHz	300 W	PE7031	86
	1 GHz	500 W	PE7032	87
	1.5 GHz	100 W	PE7021	85
	2 GHz	2 W	PE7062	89
	2 GHz	10 W	PE7010	80
	2.4 GHz	500 W	PE7085	87
	2.5 GHz	1000 W	PE7423	87
	3 GHz	1 W	PE7002	75
	3 GHz	5 W	PE7390	79
	3 GHz	10 W	PE7386	80
	3 GHz	50 W	PE7388	83
	3 GHz	100 W	PE7385	85
	3 GHz	200 W	PE7387	86
	3 GHz	500 W	PE7AP418	87
	4 GHz	2 W	PE7044	87
	4 GHz	25 W	PE7392	81
	4 GHz	50 W	PE7394	83
	4 GHz	100 W	PE7421	85
	6 GHz	5 W	PE7AP006	79
	6 GHz	50 W	PE7322	83
	6 GHz	100 W	PE7213	86
	8 GHz	25 W	PE7367	81
	8 GHz	150 W	PE7AP150	86
	8.5 GHz	250 W	PE7AP250	86
	12.4 GHz	2 W	PE7047	76
	12.4 GHz	10 W	PE7048	80
	18 GHz	2 W	PE7094	76
	18 GHz	5 W	PE7014	79
	18 GHz	10 W	PE7015	80
	18 GHz	25 W	PE7426	81
	18 GHz	50 W	PE7019	83
	18 GHz	100 W	PE7424	86

Connector In-Out	Max Freq.	Power	Model No.	Page
N Male				
N Female	18 GHz	200 W	PE7AP200	86
TNC Female	6 GHz	100 W	PE7237	86
QMA Male				
QMA Female	6 GHz	1 W	PE7AP1002	75
QN Male				
QN Female	3 GHz	1 W	PE7AP1000	75
SMA Female				
SMA Female	1 GHz	0.5 W	PE70A8000	90
	1 GHz	1 W	PE70A8001	90
	1.5 GHz	1 W	PE70A8005	90
	2 GHz	0.5 W	PE70A8002	90
	2.2 GHz	2 W	PE70A1025	89
	2.2 GHz	10 W	PE70A1031	91
	2.5 GHz	0 W	PE70A8013	90
	2.7 GHz	0 W	PE70A8014	90
	3 GHz	0.1 W	PE70A5004	91
	4 GHz	0.1 W	PE70A2000	91
	4 GHz	5 W	PE7422	90
	6 GHz	0 W	PE70A8009	91
	6 GHz	0.1 W	PE70A5000	91
	6 GHz	0.2 W	PE70A1000	91
	6 GHz	0.5 W	PE70A3902	91
	6 GHz	100 W	PE7228	86
	8 GHz	0 W	PE70A8010	91
	8 GHz	0.1 W	PE70A2001	91
	12 GHz	0.1 W	PE70A2002	91
	13 GHz	0.16 W	PE70A4000	91
	13 GHz	0.32 W	PE70A5003	90
	18 GHz	0 W	PE70A8007	90
	18 GHz	0.1 W	PE70A3900	91
	18 GHz	0.1 W	PE70A2003	91
	18 GHz	1 W	PE70A6000	91
	18 GHz	20 W	PE70A2900	91
	18 GHz	25 W	PE7363	82
	18 GHz	50 W	PE7337	84
	20 GHz	18 W	PE70A1017	91
SMA Male	6 GHz	100 W	PE7221	86
SMA Male				
SMA Female	1.5 GHz	100 W	PE7022	86
	2 GHz	2 W	PE7061	89
	3 GHz	2 W	PE7001	77
	3 GHz	5 W	PE7391	79
	4 GHz	25 W	PE7393	82
	6 GHz	2 W	PE70A1014	77
	6 GHz	10 W	PE7428	80
	6 GHz	25 W	PE7357	82
	6 GHz	100 W	PE7227	86
	12.4 GHz	2 W	PE7045	77
	18 GHz	2 W	PE7092	78
	18 GHz	5 W	PE7013	79
	18 GHz	10 W	PE7016	80
	18 GHz	25 W	PE7018	82
	18 GHz	50 W	PE7427	84
	18 GHz	100 W	PE7425	86
	26 GHz	2 W	PE7087	78
TNC Female				
N Female	6 GHz	100 W	PE7218	86
N Male	6 GHz	100 W	PE7210	86
TNC Female	18 GHz	50 W	PE7351	84
TNC Male				
TNC Female	1.5 GHz	100 W	PE7056	86
	2 GHz	1 W	PE7003	75
	2 GHz	2 W	PE7003	78
	2 GHz	2 W	PE7063	89
	12.4 GHz	2 W	PE7051	78
	18 GHz	2 W	PE7030	79
	18 GHz	5 W	PE7052	79
	18 GHz	10 W	PE7053	80
	18 GHz	25 W	PE7054	82
	18 GHz	50 W	PE7055	84

PASSIVE ATTENUATORS

Fixed Attenuators

50 Ohm






Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
0.5 W	2.92mm Male	2.92mm Female	40 GHz	Passivated Stainless Steel	1.3:1		0	PE7429-0	$259.99	See Web for Volume Pricing	1
					1.35:1		1	PE7429-1	$259.99		
							2	PE7429-2	$259.99		
							3	PE7429-3	$259.99		
							4	PE7429-4	$259.99		
							5	PE7429-5	$259.99		
							6	PE7429-6	$259.99		
							7	PE7429-7	$259.99		
							8	PE7429-8	$259.99		
							9	PE7429-9	$259.99		
							10	PE7429-10	$259.99		
							12	PE7429-12	$301.99		
							15	PE7429-15	$301.99		
							20	PE7429-20	$259.99		
							30	PE7429-30	$259.99		
					1.4:1		0	PE7AP412-00	$293.99		2
							1	PE7AP412-01	$293.99		
							2	PE7AP412-02	$293.99		
							3	PE7AP412-03	$291.99		
						Yes	3	PE7046-3	$585.00		3
							4	PE7AP412-04	$317.99		4
							5	PE7AP412-05	$305.99		
							6	PE7AP412-06	$311.99		
						Yes	6	PE7046-6	$585.00		5
							8	PE7AP412-08	$321.99		6
							9	PE7AP412-09	$305.99		
						Yes	10	PE7046-10	$565.00		7
						Yes	20	PE7046-20	$575.00		
						Yes	30	PE7046-30	$585.00		
					1.5:1		10	PE7AP412-10	$317.99		8
							12	PE7AP412-12	$301.99		
							15	PE7AP412-15	$301.99		
							20	PE7AP412-20	$317.99		
							30	PE7AP412-30	$315.99		
1 W	1.85mm Male	1.85mm Female	65 GHz	Passivated Stainless Steel	1.65:1		1	PE7403-1	$880.00	See Web for Volume Pricing	9
							2	PE7403-2	$880.00		
							3	PE7403-3	$865.00		
							4	PE7403-4	$835.00		
							5	PE7403-5	$845.00		
							6	PE7403-6	$850.00		
							7	PE7403-7	$835.00		
							8	PE7403-8	$835.00		
							9	PE7403-9	$835.00		
							10	PE7403-10	$855.00		
							20	PE7403-20	$870.00		
							30	PE7403-30	$895.00		
	2.4mm Male	2.4mm Female	50 GHz		1.75:1	Yes	0	PE7089-0	$451.99		10
						Yes	1	PE7089-1	$510.00		
						Yes	2	PE7089-2	$475.99		
						Yes	3	PE7089-3	$479.99		
						Yes	4	PE7089-4	$451.99		
						Yes	5	PE7089-5	$457.99		
						Yes	6	PE7089-6	$469.99		
						Yes	7	PE7089-7	$451.99		
						Yes	8	PE7089-8	$475.99		
						Yes	9	PE7089-9	$457.99		
						Yes	10	PE7089-10	$493.99		
						Yes	12	PE7089-12	$475.99		
						Yes	15	PE7089-15	$475.99		
						Yes	20	PE7089-20	$475.99		
						Yes	30	PE7089-30	$473.99		
	2.92mm Male	2.92mm Female	40 GHz		1.4:1	Yes	0	PE7088-0	$407.99		11
						Yes	1	PE7088-1	$389.99		
						Yes	2	PE7088-2	$405.99		
						Yes	3	PE7088-3	$357.99		
						Yes	4	PE7088-4	$407.99		
						Yes	5	PE7088-5	$407.99		

See Our Website For Current Pricing & Real-Time Stock Availability!

* Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.

Fixed Attenuators

50 Ohm






Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
1 W	2.92mm Male	2.92mm Female	40 GHz	Passivated Stainless Steel	1.4:1	Yes	6	PE7088-6	$357.99	See Web for Volume Pricing	11
						Yes	7	PE7088-7	$407.99		
						Yes	8	PE7088-8	$407.99		
						Yes	9	PE7088-9	$401.99		
						Yes	10	PE7088-10	$365.99		
						Yes	12	PE7088-12	$407.99		
						Yes	15	PE7088-15	$389.99		
						Yes	20	PE7088-20	$357.99		
						Yes	30	PE7088-30	$383.99		
	BNC Male	BNC Female	2 GHz	Nickel Plated Brass	1.2:1	Yes	1	PE7000-1	$65.99		12
						Yes	2	PE7000-2	$66.99		
						Yes	3	PE7000-3	$69.99		
						Yes	6	PE7000-6	$67.99		
						Yes	10	PE7000-10	$65.99		
						Yes	20	PE7000-20	$64.99		
						Yes	30	PE7000-30	$67.99		
	N Male	N Female	3 GHz			Yes	1	PE7002-1	$119.99		13
						Yes	2	PE7002-2	$119.99		
						Yes	3	PE7002-3	$105.99		
						Yes	6	PE7002-6	$107.99		
						Yes	10	PE7002-10	$105.99		
						Yes	20	PE7002-20	$107.99		
						Yes	30	PE7002-30	$107.99		
						Yes	40	PE7002-40	$119.99		
	QMA Male	QMA Female	6 GHz	Tri-Metal Plated Brass			0	PE7AP1002-0	$115.99		14
							1	PE7AP1002-1	$111.99		
							2	PE7AP1002-2	$111.99		
							3	PE7AP1002-3	$129.99		
							6	PE7AP1002-6	$115.99		
							9	PE7AP1002-9	$115.99		
							12	PE7AP1002-12	$111.99		
							15	PE7AP1002-15	$115.99		
							20	PE7AP1002-20	Call		
	QN Male	QN Female	3 GHz				0	PE7AP1000-0	$155.99		15
							1	PE7AP1000-1	$155.99		
							2	PE7AP1000-2	$155.99		
							3	PE7AP1000-3	$155.99		
							6	PE7AP1000-6	$163.99		
							9	PE7AP1000-9	$163.99		
							12	PE7AP1000-12	$155.99		
							15	PE7AP1000-15	$155.99		
							18	PE7AP1000-18	$155.99		
							20	PE7AP1000-20	$163.99		
	TNC Male	TNC Female	2 GHz	Nickel Plated Brass	1.2:1	Yes	1	PE7003-1	$105.99		16
						Yes	10	PE7003-10	$95.99		
						Yes	20	PE7003-20	$89.99		
						Yes	30	PE7003-30	$101.99		
						Yes	40	PE7003-40	$99.99		
2 W	2.92mm Male	2.92mm Female	26.5 GHz	Passivated Stainless Steel	1.4:1	Yes	1	PE7024-1	$383.99		17
						Yes	2	PE7024-2	$383.99		
						Yes	3	PE7024-3	$371.99		
						Yes	6	PE7024-6	$371.99		
						Yes	10	PE7024-10	$363.99		
						Yes	20	PE7024-20	$371.99		
						Yes	30	PE7024-30	$365.99		
				Stainless Steel		Yes	30	PE7024/SP-30	$251.99		18
			40 GHz	Passivated Stainless Steel	1.3:1		0	PE7430-0	$301.99		19
					1.35:1		1	PE7430-1	$301.99		
							2	PE7430-2	$301.99		
							3	PE7430-3	$301.99		
							4	PE7430-4	$301.99		
							5	PE7430-5	$301.99		
							6	PE7430-6	$301.99		
							7	PE7430-7	$301.99		
							8	PE7430-8	$301.99		
							9	PE7430-9	$301.99		
							10	PE7430-10	$301.99		
							12	PE7430-12	$321.99		
							15	PE7430-15	$321.99		

See Our Website For Current Pricing & Real-Time Stock Availability!

* Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.

Fixed Attenuators

50 Ohm






Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
2 W	2.92mm Male	2.92mm Female	40 GHz	Passivated Stainless Steel	1.35:1		20	PE7430-20	$301.99	See Web for Volume Pricing	19
							30	PE7430-30	$301.99		
					1.4:1	Yes	3	PE7090-3	$540.00		20
						Yes	10	PE7090-10	$505.00		
						Yes	15	PE7090-15	$540.00		
						Yes	20	PE7090-20	$505.00		
						Yes	30	PE7090-30	$485.99		
					1.6:1		0	PE7395-0	$231.99		21
							1	PE7395-1	$237.99		
							2	PE7395-2	$237.99		
							3	PE7395-3	$231.99		
							4	PE7395-4	$229.99		
							5	PE7395-5	$229.99		
							6	PE7395-6	$227.99		
							7	PE7395-7	$271.99		
							8	PE7395-8	$271.99		
							9	PE7395-9	$229.99		
							10	PE7395-10	$231.99		
							12	PE7395-12	$245.99		
							15	PE7395-15	$233.99		
							20	PE7395-20	$237.99		
	BNC Male	BNC Female	4 GHz	Nickel Plated Brass	1.25:1	Yes	1	PE7049-1	$145.99		22
						Yes	2	PE7049-2	$149.99		
						Yes	3	PE7049-3	$147.99		
						Yes	6	PE7049-6	$147.99		
						Yes	10	PE7049-10	$151.99		
						Yes	20	PE7049-20	$147.99		
						Yes	30	PE7049-30	$139.99		
				Tri-Metal Plated Brass			1	PE7437-1	$40.59		23
							2	PE7437-2	$40.59		
							3	PE7437-3	$40.59		
							4	PE7437-4	$40.59		
							5	PE7437-5	$40.59		
							6	PE7437-6	$40.59		
							7	PE7437-7	$40.59		
							8	PE7437-8	$40.59		
							9	PE7437-9	$40.59		
							10	PE7437-10	$40.59		
							15	PE7437-15	$40.59		
							20	PE7437-20	$40.59		
							30	PE7437-30	$40.59		
	N Male	N Female	12.4 GHz	Passivated Stainless Steel		Yes	2	PE7047-2	$215.99	See Web for Volume Pricing	24
						Yes	3	PE7047-3	$199.99		
						Yes	4	PE7047-4	$211.99		
						Yes	5	PE7047-5	$215.99		
						Yes	6	PE7047-6	$199.99		
						Yes	7	PE7047-7	$197.99		
						Yes	8	PE7047-8	$171.99		
						Yes	9	PE7047-9	$191.99		
						Yes	10	PE7047-10	$209.99		
						Yes	12	PE7047-12	$205.99		
						Yes	15	PE7047-15	$221.99		
						Yes	20	PE7047-20	$201.99		
						Yes	30	PE7047-30	$201.99		
						Yes	40	PE7047-40	$215.99		
			18 GHz		1.35:1		1	PE7094-01	$113.99		25
						Yes	1	PE7004-1	$245.99		26
							2	PE7094-02	$113.99		27
						Yes	2	PE7004-2	$271.99		28
							3	PE7094-03	$113.99		29
						Yes	3	PE7004-3	$255.99		30
							4	PE7094-04	$113.99		31
						Yes	4	PE7004-4	$275.99		32
							5	PE7094-05	$113.99		33
						Yes	5	PE7004-5	$273.99		34
							6	PE7094-06	$113.99		35
						Yes	6	PE7004-6	$251.99		36
							7	PE7094-07	$113.99		37
						Yes	7	PE7004-7	$269.99		38

See Our Website For Current Pricing & Real-Time Stock Availability!

* Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.

Fixed Attenuators

50 Ohm






Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
2 W	N Male	N Female	18 GHz	Passivated Stainless Steel	1.35:1		8	PE7094-08	$113.99	See Web for Volume Pricing	39
						Yes	8	PE7004-8	$219.99		40
							9	PE7094-09	$113.99		41
						Yes	9	PE7004-9	$239.99		42
						Yes	10	PE7004-10	$233.99		
							10	PE7094-10	$113.99		43
						Yes	12	PE7004-12	$257.99		44
							12	PE7094-12	$113.99		45
						Yes	15	PE7004-15	$263.99		46
							15	PE7094-15	$113.99		47
						Yes	20	PE7004-20	$307.99		48
							20	PE7094-20	$113.99		49
						Yes	30	PE7004-30	$253.99		50
							30	PE7094-30	$113.99		51
						Yes	40	PE7004-40	$271.99		52
							40	PE7094-40	$113.99		53
	SMA Male	SMA Female	3 GHz		1.2:1	Yes	1	PE7001-1	$117.99		54
						Yes	2	PE7001-2	$117.99		
						Yes	3	PE7001-3	$103.99		
						Yes	4	PE7001-4	$115.99		
						Yes	5	PE7001-5	$119.99		
						Yes	6	PE7001-6	$109.99		
						Yes	7	PE7001-7	$107.99		
						Yes	8	PE7001-8	$97.99		
						Yes	9	PE7001-9	$109.99		
						Yes	10	PE7001-10	$107.99		
						Yes	12	PE7001-12	$109.99		
						Yes	15	PE7001-15	$111.99		
						Yes	20	PE7001-20	$107.99		
						Yes	30	PE7001-30	$109.99		
						Yes	40	PE7001-40	$119.99		
			6 GHz	Brass	1.22:1		12	PE70A1014	$69.99		55
							16	PE70A1015	$75.99		56
				Copper	1.07:1		3	PE70A1009	$175.99		57
							6	PE70A1011	$185.99		58
					1.15:1		3	PE70A1010	$69.99		59
							6	PE70A1012	$69.99		60
				Passivated Stainless Steel	1.35:1	Yes	0	PE7091-0	$51.99		61
						Yes	1	PE7091-1	$57.99		
						Yes	1	PE7162-1	$62.99		62
						Yes	2	PE7091-2	$63.99		63
						Yes	2	PE7162-2	$61.99		64
						Yes	3	PE7091-3	$48.99		65
						Yes	3	PE7162-3	$50.99		66
						Yes	4	PE7091-4	$63.99		67
						Yes	4	PE7162-4	$60.99		68
						Yes	5	PE7091-5	$63.99		69
						Yes	5	PE7162-5	$61.99		70
						Yes	6	PE7091-6	$51.99		71
						Yes	6	PE7162-6	$40.99		72
						Yes	7	PE7091-7	$63.99		73
						Yes	7	PE7162-7	$57.99		
						Yes	8	PE7162-8	$57.99		74
						Yes	9	PE7162-9	$52.99		
						Yes	10	PE7091-10	$61.99		75
						Yes	10	PE7162-10	$46.19		76
						Yes	12	PE7091-12	$56.99		77
						Yes	12	PE7162-12	$54.99		78
						Yes	15	PE7091-15	$54.99		79
						Yes	15	PE7162-15	$55.99		80
						Yes	20	PE7091-20	$55.99		81
						Yes	20	PE7162-20	$45.99		82
						Yes	30	PE7091-30	$57.99		83
						Yes	30	PE7162-30	$54.99		84
						Yes	40	PE7091-40	$70.99		85
						Yes	40	PE7162-40	$63.99		86
			12.4 GHz		1.25:1	Yes	1	PE7045-1	$159.99		87
						Yes	2	PE7045-2	$157.99		
						Yes	3	PE7045-3	$143.99		

See Our Website For Current Pricing & Real-Time Stock Availability!

* Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.

Fixed Attenuators

50 Ohm






Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
2 W	SMA Male	SMA Female	12.4 GHz	Passivated Stainless Steel	1.25:1	Yes	4	PE7045-4	$143.99	See Web for Volume Pricing	87
						Yes	5	PE7045-5	$159.99		
						Yes	6	PE7045-6	$145.99		
						Yes	7	PE7045-7	$135.99		
						Yes	8	PE7045-8	$121.99		
						Yes	9	PE7045-9	$135.99		
						Yes	10	PE7045-10	$141.99		
						Yes	12	PE7045-12	$135.99		
						Yes	15	PE7045-15	$147.99		
						Yes	20	PE7045-20	$147.99		
						Yes	30	PE7045-30	$147.99		
						Yes	40	PE7045-40	$155.99		
			18 GHz		1.35:1	Yes	1	PE7092-1	$62.99		88
						Yes	1	PE7005-1	$85.99		89
						Yes	2	PE7092-2	$62.99		90
						Yes	2	PE7005-2	$80.99		91
						Yes	3	PE7092-3	$53.99		92
						Yes	3	PE7005-3	$77.99		93
						Yes	4	PE7092-4	$63.99		94
						Yes	4	PE7005-4	$93.99		95
						Yes	5	PE7092-5	$64.99		96
						Yes	5	PE7005-5	$91.99		97
						Yes	6	PE7092-6	$51.99		98
						Yes	6	PE7005-6	$82.99		99
						Yes	7	PE7092-7	$69.99		1
						Yes	7	PE7005-7	$94.99		2
						Yes	8	PE7092-8	$60.99		3
						Yes	8	PE7005-8	$94.99		4
						Yes	9	PE7092-9	$54.99		5
						Yes	9	PE7005-9	$83.99		6
						Yes	10	PE7005-10	$77.99		
						Yes	10	PE7092-10	$56.99		7
						Yes	12	PE7005-12	$88.99		8
						Yes	12	PE7092-12	$55.99		9
						Yes	15	PE7005-15	$77.99		10
						Yes	15	PE7092-15	$62.99		11
						Yes	20	PE7005-20	$77.99		12
						Yes	20	PE7092-20	$64.99		13
						Yes	30	PE7005-30	$80.99		14
						Yes	30	PE7092-30	$55.99		15
						Yes	40	PE7005-40	$86.99		16
						Yes	40	PE7092-40	$82.99		17
			26 GHz		1.4:1	Yes	0	PE7087-0	$127.99		18
						Yes	1	PE7087-1	$143.99		
						Yes	2	PE7087-2	$143.99		
						Yes	3	PE7087-3	$125.99		
						Yes	4	PE7087-4	$145.99		
						Yes	5	PE7087-5	$139.99		
						Yes	6	PE7087-6	$125.99		
						Yes	7	PE7087-7	$135.99		
						Yes	8	PE7087-8	$145.99		
						Yes	9	PE7087-9	$133.99		
						Yes	10	PE7087-10	$123.99		
						Yes	12	PE7087-12	$135.99		
						Yes	15	PE7087-15	$143.99		
						Yes	20	PE7087-20	$125.99		
						Yes	30	PE7087-30	$125.99		
	TNC Male	TNC Female	2 GHz	Nickel Plated Brass	1.15:1	Yes	2	PE7003-2	$93.99		19
						Yes	3	PE7003-3	$88.99		
						Yes	6	PE7003-6	$98.99		
			12.4 GHz		1.25:1	Yes	1	PE7051-1	$215.99		20
						Yes	2	PE7051-2	$215.99		
						Yes	3	PE7051-3	$191.99		
						Yes	6	PE7051-6	$197.99		
						Yes	10	PE7051-10	$197.99		
						Yes	20	PE7051-20	$197.99		
						Yes	30	PE7051-30	$213.99		
						Yes	40	PE7051-40	$197.99		

See Our Website For Current Pricing & Real-Time Stock Availability!

* Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.

Fixed Attenuators

50 Ohm






Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
2 W	TNC Male	TNC Female	18 GHz	Passivated Stainless Steel	1.35:1	Yes	1	PE7030-1	$311.99		21
						Yes	2	PE7030-2	$355.99		
						Yes	3	PE7030-3	$369.99		
						Yes	6	PE7030-6	$369.99		
						Yes	10	PE7030-10	$375.99		
						Yes	20	PE7030-20	$373.99		
						Yes	30	PE7030-30	$345.99		
5 W	7/16 DIN Male	7/16 DIN Female	7.5 GHz	Tri-Metal Plated Brass	1.25:1	Yes	3	PE7039-3	$259.99		22
						Yes	6	PE7039-6	$259.99		
						Yes	10	PE7039-10	Call		
						Yes	20	PE7039-20	$259.99		
						Yes	30	PE7039-30	$335.99		
	N Male	N Female	3 GHz	Aluminum	1.2:1	Yes	1	PE7390-1	$85.99		23
						Yes	2	PE7390-2	$85.99		
						Yes	3	PE7390-3	$79.99		
						Yes	6	PE7390-6	$79.99		
						Yes	10	PE7390-10	$80.99		
						Yes	15	PE7390-15	$78.99		
						Yes	20	PE7390-20	$79.99		
						Yes	30	PE7390-30	$78.99		
			6 GHz	Black Anodized Aluminum Heatsink	1.25:1		1	PE7AP006-01	$151.99	See Web for Volume Pricing	24
							2	PE7AP006-02	$157.99		
							3	PE7AP006-03	$149.99		
							4	PE7AP006-04	$157.99		
							5	PE7AP006-05	$157.99		
							6	PE7AP006-06	$149.99		
							9	PE7AP006-09	$145.99		
							10	PE7AP006-10	$151.99		
							12	PE7AP006-12	$145.99		
							15	PE7AP006-15	$137.99		
							20	PE7AP006-20	$191.99		
							30	PE7AP006-30	$151.99		
							40	PE7AP006-40	$167.99		
			18 GHz		1.4:1	Yes	1	PE7014-1	$369.99		25
						Yes	2	PE7014-2	$369.99		
						Yes	3	PE7014-3	$387.99		
						Yes	6	PE7014-6	$387.99		
						Yes	10	PE7014-10	$359.99		
						Yes	20	PE7014-20	$387.99		
						Yes	30	PE7014-30	$379.99		
						Yes	40	PE7014-40	$401.99		
	SMA Male	SMA Female	3 GHz	Aluminum	1.2:1	Yes	6	PE7391-6	$78.99		26
						Yes	10	PE7391-10	$78.99		
						Yes	20	PE7391-20	$79.99		
						Yes	30	PE7391-30	$78.99		
				Black Anodized Aluminum Heatsink		Yes	1	PE7391-1	$82.99	See Web for Volume Pricing	
						Yes	2	PE7391-2	$85.99		
						Yes	3	PE7391-3	$78.99		
						Yes	15	PE7391-15	$78.99		
			18 GHz		1.35:1	Yes	1	PE7013-1	$219.99		27
						Yes	2	PE7013-2	$229.99		
						Yes	3	PE7013-3	$205.99		
						Yes	6	PE7013-6	$213.99		
						Yes	10	PE7013-10	$197.99		
						Yes	20	PE7013-20	$191.99		
						Yes	30	PE7013-30	$207.99		
						Yes	40	PE7013-40	$229.99		
	TNC Male	TNC Female				Yes	1	PE7052-1	$367.99		28
						Yes	2	PE7052-2	$381.99		
						Yes	3	PE7052-3	$381.99		
						Yes	6	PE7052-6	$381.99		
						Yes	10	PE7052-10	$381.99		
						Yes	20	PE7052-20	$381.99		
						Yes	30	PE7052-30	$381.99		
10 W	2.92mm Male	2.92mm Female	40 GHz	Black Anodized Aluminum Heatsink	1.4:1	No	3	PE7AP4009-03	$925.00		29
						Yes	3	PE7AP402-3	$1,190.00		30
						No	6	PE7AP4009-06	$925.00		31
						Yes	6	PE7AP402-6	$1,190.00		32

* Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Attenuators

50 Ohm






Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
10 W	2.92mm Male	2.92mm Female	40 GHz	Black Anodized Aluminum Heatsink	1.4:1	No	10	PE7AP4009-10	$925.00	See Web for Volume Pricing	33
						No	10	PE7AP402-10	$1,110.00		34
						No	20	PE7AP4009-20	$925.00		35
						No	20	PE7AP402-20	$1,140.00		36
						No	30	PE7AP4009-30	$925.00		37
						No	30	PE7AP402-30	$1,210.00		38
						No	40	PE7AP4009-40	$1,040.00		39
	7/16 DIN Male	7/16 DIN Female	7.5 GHz		1.45:1	Yes	6	PE7040-6	$367.99		40
						Yes	10	PE7040-10	$425.99		
						Yes	20	PE7040-20	$241.99		
	BNC Male	BNC Female	2 GHz		1.6:1	Yes	2	PE7025-2	$395.99		41
						Yes	3	PE7025-3	$415.99		
						Yes	6	PE7025-6	$405.99		
						Yes	10	PE7025-10	$407.99		
						Yes	20	PE7025-20	$401.99		
						Yes	30	PE7025-30	$389.99		
						Yes	40	PE7025-40	$457.99		
	N Male	N Female				Yes	2	PE7010-2	$325.99		42
						Yes	3	PE7010-3	$327.99		
						Yes	6	PE7010-6	$301.99		
						Yes	10	PE7010-10	$327.99		
						Yes	20	PE7010-20	$327.99		
						Yes	30	PE7010-30	$301.99		
						Yes	40	PE7010-40	$251.99		
			3 GHz		1.2:1	Yes	3	PE7386-3	$181.99		43
						Yes	6	PE7386-6	$183.99		
						Yes	10	PE7386-10	$183.99		
						Yes	15	PE7386-15	$151.99		
						Yes	20	PE7386-20	$183.99		
						Yes	30	PE7386-30	$183.99		
						Yes	40	PE7386-40	$197.99		
			12.4 GHz		1.35:1	Yes	1	PE7048-1	$479.99		44
						Yes	2	PE7048-2	$479.99		
						Yes	3	PE7048-3	$473.99		
						Yes	6	PE7048-6	$471.99		
						Yes	10	PE7048-10	$473.99		
						Yes	20	PE7048-20	$465.99		
						Yes	30	PE7048-30	$453.99		
						Yes	40	PE7048-40	$473.99		
			18 GHz		1.4:1	Yes	1	PE7015-1	$363.99		45
						Yes	2	PE7015-2	$379.99		
						Yes	3	PE7015-3	$465.99		
						Yes	6	PE7015-6	$467.99		
						Yes	10	PE7015-10	$459.99		
						Yes	20	PE7015-20	$451.99		
						Yes	30	PE7015-30	$467.99		
						Yes	40	PE7015-40	$479.99		
	SMA Male	SMA Female	6 GHz		1.2:1		1	PE7428-01	$215.99	See Web for Volume Pricing	46
							2	PE7428-02	$197.99		
							3	PE7428-03	$217.99		
							6	PE7428-06	$253.99		
							10	PE7428-10	$189.99		
							15	PE7428-15	$199.99		
							20	PE7428-20	$203.99		
							30	PE7428-30	$179.99		
			18 GHz		1.4:1	Yes	1	PE7016-1	$465.99		47
						Yes	2	PE7016-2	$425.99		
						Yes	3	PE7016-3	$439.99		
						Yes	6	PE7016-6	$431.99		
						Yes	10	PE7016-10	$429.99		
						Yes	20	PE7016-20	$431.99		
						Yes	30	PE7016-30	$439.99		
						Yes	40	PE7016-40	$465.99		
	TNC Male	TNC Female				Yes	6	PE7053-6	$535.00		48
						Yes	10	PE7053-10	$550.00		
						Yes	20	PE7053-20	$595.00		
						Yes	40	PE7053-40	$585.00		
15 W	4.3-10 Male	4.3-10 Female	6 GHz	Aluminum	1.15:1		3	PE7AP1001-3	$361.99		49
							6	PE7AP1001-6	$361.99		

* Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Attenuators

50 Ohm






Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
15 W	4.3-10 Male	4.3-10 Female	6 GHz	Aluminum	1.15:1		10	PE7AP1001-10	$395.99		49
							20	PE7AP1001-20	$361.99		
25 W	7/16 DIN Female	7/16 DIN Female	6 GHz	Black Anodized Aluminum Heatsink	1.3:1	Yes	50	PE7380-50	$555.00	See Web for Volume Pricing	50
			7.5 GHz		1.45:1	Yes	3	PE7380-3	$555.00		
						Yes	6	PE7380-6	$555.00		
						Yes	10	PE7380-10	$555.00		
						Yes	20	PE7380-20	$555.00		
						Yes	30	PE7380-30	$555.00		
						Yes	40	PE7380-40	$555.00		
	7/16 DIN Male		6 GHz		1.3:1	Yes	50	PE7379-50	$550.00		51
			7.5 GHz		1.45:1	Yes	3	PE7379-3	$560.00		
						Yes	6	PE7379-6	$550.00		
						Yes	10	PE7041-10	Call		52
						Yes	10	PE7379-10	$720.00		53
						Yes	20	PE7379-20	$575.00		
						Yes	30	PE7379-30	$550.00		
						Yes	40	PE7379-40	$550.00		
	N Female		6 GHz		1.3:1	Yes	50	PE7369-50	$483.99		54
			7.5 GHz		1.45:1	Yes	3	PE7369-3	$483.99		
						Yes	6	PE7369-6	$483.99		
						Yes	10	PE7369-10	$483.99		
						Yes	20	PE7369-20	$483.99		
						Yes	30	PE7369-30	$483.99		
						Yes	40	PE7369-40	$483.99		
		7/16 DIN Male	6 GHz		1.3:1	Yes	50	PE7370-50	$475.99		55
			7.5 GHz		1.45:1	Yes	3	PE7370-3	$475.99		
						Yes	6	PE7370-6	$475.99		
						Yes	10	PE7370-10	$475.99		
						Yes	20	PE7370-20	$475.99		
						Yes	30	PE7370-30	$475.99		
						Yes	40	PE7370-40	$475.99		
		N Female	8 GHz		1.6:1	Yes	50	PE7371-50	$453.99		56
			18 GHz		1.45:1	Yes	10	PE7371-10	$535.00		
					1.6:1	Yes	3	PE7371-3	$535.00		
						Yes	6	PE7371-6	$535.00		
						Yes	20	PE7371-20	$535.00		
						Yes	30	PE7371-30	$535.00		
						Yes	40	PE7371-40	$555.00		
		TNC Female				Yes	30	PE7372-30	Call		57
	N Male	7/16 DIN Female	6 GHz		1.3:1	Yes	50	PE7366-50	$485.99		58
			7.5 GHz		1.45:1	Yes	3	PE7366-3	$485.99		
						Yes	6	PE7366-6	$485.99		
						Yes	10	PE7366-10	$485.99		
						Yes	20	PE7366-20	$485.99		
						Yes	30	PE7366-30	$515.00		
						Yes	40	PE7366-40	$515.00		
		N Female	4 GHz		1.25:1	Yes	1	PE7392-1	$263.99		59
						Yes	2	PE7392-2	$263.99		
						Yes	3	PE7392-3	$247.99		
						Yes	6	PE7392-6	$249.99		
						Yes	10	PE7392-10	$249.99		
						Yes	20	PE7392-20	$251.99		
						Yes	30	PE7392-30	$251.99		
						Yes	40	PE7392-40	$263.99		
			8 GHz		1.6:1	Yes	50	PE7367-50	$570.00		60
			18 GHz		1.35:1	Yes	3	PE7426-03	$393.99		61
						Yes	6	PE7426-06	$399.99		
						Yes	10	PE7426-10	$409.99		
						Yes	20	PE7426-20	$423.99		
						Yes	30	PE7426-30	$399.99		
						Yes	40	PE7426-40	$433.99		
					1.4:1	Yes	1	PE7017-1	$675.00		62
						Yes	2	PE7017-2	$775.00		
						Yes	3	PE7017-3	$685.00		
						Yes	6	PE7017-6	$680.00		
						Yes	10	PE7017-10	$685.00		
						Yes	20	PE7017-20	$675.00		

See Our Website For Current Pricing & Real-Time Stock Availability!

* Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.

Fixed Attenuators

50 Ohm





Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
25 W	N Male	N Female	18 GHz	Black Anodized Aluminum Heatsink	1.4:1	Yes	30	PE7017-30	$655.00	See Web for Volume Pricing	62
						Yes	40	PE7017-40	$790.00		
					1.45:1	Yes	10	PE7367-10	$565.00		63
					1.6:1	Yes	3	PE7367-3	$565.00		
						Yes	6	PE7367-6	$565.00		
						Yes	20	PE7367-20	$565.00		
						Yes	30	PE7367-30	$550.00		
						Yes	40	PE7367-40	$570.00		
	SMA Female	SMA Female				Yes	6	PE7363-6	$505.00		64
						Yes	10	PE7363-10	$515.00		
						Yes	20	PE7363-20	$515.00		
						Yes	30	PE7363-30	$515.00		
						Yes	40	PE7363-40	$555.00		
	SMA Male		4 GHz		1.25:1	Yes	3	PE7393-3	$193.99		65
						Yes	10	PE7393-10	$239.99		
						Yes	20	PE7393-20	$239.99		
						Yes	30	PE7393-30	$239.99		
						Yes	40	PE7393-40	$259.99		
			6 GHz		1.3:1	Yes	50	PE7357-50	$419.99		66
			18 GHz		1.4:1	Yes	1	PE7018-1	$695.00		67
						Yes	2	PE7018-2	$660.00		
						Yes	3	PE7018-3	$755.00		
						Yes	6	PE7018-6	$740.00		
						Yes	10	PE7018-10	$770.00		
						Yes	20	PE7018-20	$665.00		
						Yes	30	PE7018-30	$770.00		
						Yes	40	PE7018-40	$805.00		
					1.6:1	Yes	3	PE7357-3	$515.00		68
						Yes	6	PE7357-6	$399.99		
						Yes	10	PE7357-10	$515.00		
						Yes	20	PE7357-20	$505.00		
						Yes	30	PE7357-30	$515.00		
						Yes	40	PE7357-40	$530.00		
	TNC Male	TNC Female			1.4:1	Yes	10	PE7054-10	$950.00		69
						Yes	20	PE7054-20	Call		
						Yes	30	PE7054-30	$900.00		
					1.6:1	Yes	20	PE7375-20	$493.99		70
						Yes	30	PE7375-30	$469.99		
						Yes	40	PE7375-40	$487.99		
50 W	7/16 DIN Female	7/16 DIN Female	6 GHz	Black Anodized Aluminum Heatsink	1.3:1	No	50	PE7313-50	$615.00	See Web for Volume Pricing	71
			7.5 GHz		1.45:1	No	3	PE7313-3	$615.00		
						No	6	PE7313-6	$725.00		
						No	10	PE7313-10	$615.00		
						No	20	PE7313-20	$615.00		
						No	30	PE7313-30	$615.00		
						No	40	PE7313-40	$725.00		
		7/16 DIN Male	6 GHz		1.3:1	No	50	PE7310-50	$605.00		72
			7.5 GHz		1.45:1	No	3	PE7310-3	$635.00		
						No	6	PE7310-6	$605.00		
						No	10	PE7310-10	$635.00		
						No	20	PE7310-20	$605.00		
						No	30	PE7310-30	$605.00		
						No	40	PE7310-40	$605.00		
		N Female	6 GHz		1.3:1	No	50	PE7316-50	$570.00		73
						No	50	PE7321-50	$540.00		74
			7.5 GHz		1.45:1	No	3	PE7316-3	$545.00		75
						No	6	PE7316-6	$545.00		
						No	10	PE7316-10	$545.00		
						No	20	PE7316-20	$545.00		
						No	30	PE7316-30	$545.00		
						No	40	PE7316-40	$545.00		
			18 GHz		1.6:1	No	3	PE7321-3	$540.00		76
						No	6	PE7321-6	$540.00		
						No	10	PE7321-10	$540.00		
						No	20	PE7321-20	$540.00		
						No	30	PE7321-30	$540.00		
						No	40	PE7321-40	$540.00		
	7/16 DIN Male	7/16 DIN Female	6 GHz		1.3:1	No	50	PE7312-50	$605.00		77
			7.5 GHz		1.45:1	No	3	PE7312-3	$635.00		
						No	6	PE7312-6	$605.00		

* Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Attenuators

50 Ohm






Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
50 W	7/16 DIN Male	7/16 DIN Female	7.5 GHz	Black Anodized Aluminum Heatsink	1.45:1	No	10	PE7042-10	$830.00	See Web for Volume Pricing	78
						No	10	PE7312-10	$635.00		79
						No	20	PE7312-20	$640.00		
						No	30	PE7042-30	$765.00		80
						No	30	PE7312-30	$605.00		
						No	40	PE7312-40	$605.00		81
	N Female		6 GHz		1.3:1	No	50	PE7315-50	$540.00		
			7.5 GHz		1.45:1	No	3	PE7315-3	$540.00		82
						No	6	PE7315-6	$540.00		
						No	10	PE7315-10	$540.00		
						No	20	PE7315-20	$540.00		
						No	30	PE7315-30	$540.00		
						No	40	PE7315-40	$570.00		
		7/16 DIN Male	6 GHz		1.3:1	No	50	PE7311-50	$565.00		
			7.5 GHz		1.45:1	No	3	PE7311-3	$535.00		83
						No	6	PE7311-6	$535.00		
						No	10	PE7311-10	$535.00		
						No	20	PE7311-20	$555.00		
						No	30	PE7311-30	$555.00		
						No	40	PE7311-40	$535.00		
		N Female	6 GHz		1.3:1	No	50	PE7323-50	$550.00		
			18 GHz		1.6:1	No	3	PE7323-3	$575.00		84
						No	6	PE7323-6	$575.00		
						No	10	PE7323-10	$670.00		
						No	20	PE7323-20	$765.00		
						No	30	PE7323-30	$670.00		
						No	40	PE7323-40	$675.00		
		N Male	6 GHz		1.3:1	No	50	PE7317-50	$680.00		
			18 GHz		1.6:1	No	3	PE7317-3	$650.00		85
						No	6	PE7317-6	$660.00		
						No	10	PE7317-10	$660.00		
						No	20	PE7317-20	$685.00		
						No	30	PE7317-30	$660.00		
						No	40	PE7317-40	$675.00		
	N Male	7/16 DIN Female	6 GHz		1.3:1	No	50	PE7314-50	$545.00		
			7.5 GHz		1.45:1	No	3	PE7314-3	$545.00		86
						No	6	PE7314-6	$545.00		
						No	10	PE7314-10	$545.00		
						No	20	PE7314-20	$545.00		
						No	30	PE7314-30	$550.00		
						No	40	PE7314-40	$545.00		
		N Female	3 GHz		1.15:1	No	3	PE7388-3	$315.99		87
						Yes	3	PE7389-3	$275.99		88
						No	6	PE7388-6	$315.99		89
						Yes	6	PE7389-6	$275.99		90
						No	10	PE7388-10	$323.99		91
						Yes	10	PE7389-10	$275.99		92
						No	15	PE7388-15	$323.99		93
						Yes	15	PE7389-15	$275.99		94
						No	20	PE7388-20	$325.99		95
						Yes	20	PE7389-20	$273.99		96
						No	30	PE7388-30	$311.99		97
						Yes	30	PE7389-30	$277.99		98
						No	40	PE7388-40	$347.99		99
						Yes	40	PE7389-40	$291.99		1
			4 GHz		1.35:1	Yes	2	PE7394-2	$363.99		
						Yes	3	PE7394-3	$423.99		2
						Yes	6	PE7394-6	$343.99		
						Yes	10	PE7394-10	$343.99		
						Yes	30	PE7394-30	$361.99		
						Yes	40	PE7394-40	$363.99		
			6 GHz		1.3:1	No	50	PE7322-50	$580.00		3
			18 GHz		1.45:1	No	6	PE7019-6	$745.00		
						No	10	PE7019-10	$820.00		4
						No	20	PE7019-20	$820.00		
						No	30	PE7019-30	$820.00		
						No	40	PE7019-40	$755.00		
					1.6:1	No	3	PE7322-3	$660.00		
						No	6	PE7322-6	$660.00		5

* Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Attenuators

50 Ohm






Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
50 W	N Male	N Female	18 GHz	Black Anodized Aluminum Heatsink	1.6:1	No	10	PE7322-10	$660.00	See Web for Volume Pricing	5
						No	20	PE7322-20	$765.00		
						No	30	PE7322-30	$665.00		
						No	40	PE7322-40	$580.00		
	SMA Female	SMA Female				No	6	PE7337-6	$640.00		6
						No	10	PE7337-10	$640.00		
						No	20	PE7337-20	$640.00		
						No	30	PE7337-30	$640.00		
						No	40	PE7337-40	$660.00		
						No	50	PE7337-50	$760.00		
	SMA Male				1.35:1	Yes	3	PE7427-03	$680.00		7
						Yes	10	PE7427-10	$670.00		
						Yes	15	PE7427-15	$640.00		
						Yes	20	PE7427-20	$670.00		
						Yes	30	PE7427-30	$670.00		
						Yes	40	PE7427-40	$670.00		
					1.45:1	Yes	6	PE7427-06	$670.00		
						No	6	PE7020-6	$885.00		8
						No	10	PE7020-10	$885.00		
						No	20	PE7020-20	$745.00		
						No	30	PE7020-30	$805.00		
						No	40	PE7020-40	$800.00		
	TNC Female	TNC Female			1.6:1	No	10	PE7351-10	$615.00		9
						No	20	PE7351-20	$615.00		
						No	40	PE7351-40	$735.00		
						No	50	PE7351-50	$645.00		
	TNC Male				1.45:1	No	30	PE7055-30	$965.00		10
						No	40	PE7055-40	$935.00		
100 W	7/16 DIN Female	7/16 DIN Female	6 GHz	Black Anodized Aluminum Heatsink	1.45:1	No	3	PE7204-3	$980.00		11
						No	6	PE7204-6	$980.00		
						No	10	PE7204-10	$980.00		
						No	20	PE7204-20	$980.00		
						No	30	PE7204-30	$980.00		
						No	40	PE7204-40	$1,050.00		
						No	50	PE7204-50	$1,050.00		
						No	60	PE7204-60	$1,050.00		
		7/16 DIN Male				No	3	PE7201-3	$985.00		12
						No	6	PE7201-6	$985.00		
						No	10	PE7201-10	$1,030.00		
						No	20	PE7201-20	$1,020.00		
						No	30	PE7201-30	$975.00		
						No	40	PE7201-40	$1,040.00		
						No	50	PE7201-50	$1,040.00		
						No	60	PE7201-60	$1,060.00		
		N Female				No	3	PE7212-3	$900.00		13
						No	6	PE7212-6	$900.00		
						No	10	PE7212-10	$900.00		
						No	20	PE7212-20	$900.00		
						No	30	PE7212-30	$900.00		
						No	40	PE7212-40	$965.00		
						No	50	PE7212-50	$965.00		
						No	60	PE7212-60	$965.00		
		N Male				No	3	PE7207-3	$900.00		14
						No	6	PE7207-6	$900.00		
						No	10	PE7207-10	$900.00		
						No	20	PE7207-20	$900.00		
						No	30	PE7207-30	$900.00		
						No	40	PE7207-40	$965.00		
						No	50	PE7207-50	$965.00		
						No	60	PE7207-60	$965.00		
	7/16 DIN Male	7/16 DIN Female				No	3	PE7203-3	$1,030.00		15
						No	6	PE7203-6	$975.00		
						No	10	PE7203-10	$1,030.00		
						No	20	PE7203-20	$1,080.00		
						No	30	PE7203-30	$975.00		
						No	40	PE7203-40	$1,100.00		
						No	50	PE7203-50	$1,100.00		
						No	60	PE7203-60	$1,190.00		
		N Female				No	3	PE7211-3	$890.00		16

See Our Website For Current Pricing & Real-Time Stock Availability!

* Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.

Fixed Attenuators

50 Ohm






Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
100 W	7/16 DIN Male	N Female	6 GHz	Black Anodized Aluminum Heatsink	1.45:1	No	6	PE7211-6	$890.00	See Web for Volume Pricing	16
						No	10	PE7211-10	$890.00		
						No	20	PE7211-20	$890.00		
						No	30	PE7211-30	$935.00		
						No	40	PE7211-40	$1,180.00		
						No	50	PE7211-50	$1,180.00		
						No	60	PE7211-60	$955.00		
	BNC Male	BNC Female	1,000 MHz		1.4:1	No	3	PE7026-3	$1,070.00		17
						No	6	PE7026-6	$1,080.00		
						No	10	PE7026-10	$950.00		
						No	20	PE7026-20	$1,140.00		
						No	30	PE7026-30	$990.00		
						No	40	PE7026-40	$1,140.00		
	N Female	7/16 DIN Female	6 GHz		1.45:1	No	3	PE7206-3	$1,060.00		18
						No	6	PE7206-6	$900.00		
						No	10	PE7206-10	$900.00		
						No	20	PE7206-20	$1,060.00		
						No	30	PE7206-30	$900.00		
						No	40	PE7206-40	$965.00		
						No	50	PE7206-50	$965.00		
						No	60	PE7206-60	$965.00		
		7/16 DIN Male				No	3	PE7202-3	$890.00		19
						No	6	PE7202-6	$890.00		
						No	10	PE7202-10	$890.00		
						No	20	PE7202-20	$890.00		
						No	30	PE7202-30	$940.00		
						No	40	PE7202-40	$955.00		
						No	50	PE7202-50	$955.00		
						No	60	PE7202-60	$955.00		
		N Female				No	3	PE7214-3	$960.00		20
						No	6	PE7214-6	$940.00		
						No	10	PE7214-10	$950.00		
						No	20	PE7214-20	$960.00		
						No	30	PE7214-30	$960.00		
						No	40	PE7214-40	$975.00		
						No	50	PE7214-50	$1,020.00		
						No	60	PE7214-60	$990.00		
		N Male				No	3	PE7208-3	$905.00		21
						No	6	PE7208-6	$965.00		
						No	10	PE7208-10	$905.00		
						No	20	PE7208-20	$970.00		
						No	30	PE7208-30	$930.00		
						No	40	PE7208-40	$990.00		
						No	50	PE7208-50	$980.00		
						No	60	PE7208-60	$980.00		
	N Male	7/16 DIN Female				No	3	PE7205-3	$900.00	See Web for Volume Pricing	22
						No	6	PE7205-6	$900.00		
						No	10	PE7205-10	$900.00		
						No	20	PE7205-20	$900.00		
						No	30	PE7205-30	$900.00		
						No	40	PE7205-40	$965.00		
						No	50	PE7205-50	$965.00		
						No	60	PE7205-60	$965.00		
		N Female	1.5 GHz		1.25:1	No	6	PE7021-6	$1,110.00		23
						No	10	PE7021-10	$920.00		
						No	20	PE7021-20	$950.00		
						No	30	PE7021-30	$975.00		
						No	40	PE7021-40	$1,010.00		
			3 GHz		1.3:1	Yes	3	PE7385-3	$555.00		24
						Yes	6	PE7385-6	$555.00		
						Yes	10	PE7385-10	$555.00		
						Yes	20	PE7385-20	$555.00		
						Yes	30	PE7385-30	$555.00		
						Yes	40	PE7385-40	$570.00		
			4 GHz		1.2:1	Yes	3	PE7421-3	$650.00		25
						Yes	6	PE7421-6	$650.00		
						Yes	10	PE7421-10	$660.00		
						Yes	20	PE7421-20	$650.00		
						Yes	30	PE7421-30	$700.00		

* Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Attenuators

50 Ohm






Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
100 W	N Male	N Female	4 GHz	Black Anodized Aluminum Heatsink	1.2:1	No	40	PE7421-40	$810.00	See Web for Volume Pricing	25
			6 GHz		1.45:1	No	3	PE7213-3	$865.00		26
						No	6	PE7213-6	$940.00		
						No	10	PE7213-10	$970.00		
						No	20	PE7213-20	$975.00		
						No	30	PE7213-30	$960.00		
						No	40	PE7213-40	$990.00		
						No	50	PE7213-50	$1,010.00		
						No	60	PE7213-60	$980.00		
			18 GHz		1.35:1	No	10	PE7424-10	$1,080.00		27
						No	20	PE7424-20	$1,150.00		
						No	30	PE7424-30	$1,170.00		
						No	40	PE7424-40	$1,180.00		
					1.45:1	No	3	PE7424-03	$1,270.00		
						No	6	PE7424-06	$1,110.00		
		TNC Female	6 GHz			No	30	PE7237-30	$870.00		28
	SMA Female	SMA Female				No	3	PE7228-3	Call		29
						No	20	PE7228-20	$915.00		
						No	30	PE7228-30	$960.00		
		SMA Male				No	3	PE7221-3	$820.00		30
						No	6	PE7221-6	$850.00		
						No	10	PE7221-10	$860.00		
						No	20	PE7221-20	$860.00		
						No	40	PE7221-40	$935.00		
						No	50	PE7221-50	$890.00		
						No	60	PE7221-60	$970.00		
	SMA Male	SMA Female	1.5 GHz		1.25:1	No	6	PE7022-6	$1,070.00		31
						No	10	PE7022-10	Call		
						No	20	PE7022-20	$765.00		
						No	30	PE7022-30	$1,070.00		
						No	40	PE7022-40	$985.00		
			6 GHz		1.45:1	No	3	PE7227-3	Call		32
						No	6	PE7227-6	Call		
						No	10	PE7227-10	Call		
						No	20	PE7227-20	Call		
						No	30	PE7227-30	Call		
						No	40	PE7227-40	Call		
						No	50	PE7227-50	Call		
						No	60	PE7227-60	Call		
			18 GHz		1.35:1	No	10	PE7425-10	$1,230.00		33
						No	20	PE7425-20	$1,140.00		
						No	30	PE7425-30	$1,170.00		
						No	40	PE7425-40	$1,210.00		
	TNC Female	N Female	6 GHz		1.45:1	No	3	PE7218-3	$845.00		34
		N Male				No	30	PE7210-30	Call		35
	TNC Male	TNC Female	1.5 GHz		1.15:1	No	30	PE7056-30	$1,040.00		36
150 W	N Male	N Female	8 GHz	Black Anodized Aluminum Heatsink	1.5:1	No	3	PE7AP150-03	$840.00		37
						No	6	PE7AP150-06	$825.00		
						No	10	PE7AP150-10	$870.00		
						No	20	PE7AP150-20	$870.00		
						No	30	PE7AP150-30	$925.00		
						No	40	PE7AP150-40	$870.00		
200 W	N Male	N Female	3 GHz	Black Anodized Aluminum Heatsink	1.35:1	No	10	PE7387-10	$790.00		38
						No	20	PE7387-20	$795.00		
						No	30	PE7387-30	$795.00		
						No	40	PE7387-40	$820.00		
			18 GHz		1.5:1	No	20	PE7AP200-20	$3,400.00		39
250 W	N Male	N Female	8.5 GHz	Black Anodized Aluminum Heatsink	1.45:1	No	10	PE7AP250-10	$1,060.00		40
						No	20	PE7AP250-20	$1,100.00		
						No	30	PE7AP250-30	$1,100.00		
						No	40	PE7AP250-40	$1,190.00		
300 W	N Male	N Female	1,000 MHz	Black Anodized Aluminum Heatsink	1.4:1	No	3	PE7031-3	Call		41
						No	10	PE7031-10	Call		
						No	30	PE7031-30	Call		

See Our Website For Current Pricing & Real-Time Stock Availability!

* Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.

Fixed Attenuators

50 Ohm





Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
500 W	N Male	N Female	1,000 MHz	Black Anodized Aluminum Heatsink	1.15:1	No	6	PE7032-6	Call	See Web for Volume Pricing	42
			2.4 GHz		1.35:1	No	2	PE7085-2	$2,910.00		43
						No	20	PE7085-20	$2,380.00		
			3 GHz			No	10	PE7AP418-10	$2,420.00		44
						No	20	PE7AP418-20	$2,420.00		
						No	30	PE7AP418-30	$2,420.00		
						No	40	PE7AP418-40	$2,420.00		
					1.4:1	No	3	PE7AP418-03	$2,420.00		
1000 W	N Male	N Female	2.5 GHz	Black Aluminum Heatsink	1.35:1	No	30	PE7423-30	$4,650.00		45
						No	40	PE7423-40	$4,650.00		

75 Ohm






Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
1 W	BNC Male	BNC Female	1,000 MHz	Nickel Plated Brass	1.2:1	Yes	1	PE7009-1	$80.99	See Web for Volume Pricing	46
						Yes	2	PE7009-2	$80.99		
						Yes	3	PE7009-3	$72.99		
						Yes	6	PE7009-6	$74.99		
						Yes	10	PE7009-10	$73.99		
						Yes	20	PE7009-20	$73.99		
						Yes	30	PE7009-30	$73.99		
	N Male	N Female				Yes	3	PE7029-3	$97.99		47
						Yes	6	PE7029-6	$88.99		
						Yes	10	PE7029-10	$109.99		
						Yes	20	PE7029-20	$87.99		
						Yes	30	PE7029-30	Call		
2 W	BNC Male	BNC Female	4 GHz	Nickel Plated Brass	1.35:1	Yes	2	PE7050-2	$171.99		48
						Yes	3	PE7050-3	$157.99		
						Yes	6	PE7050-6	$157.99		
						Yes	10	PE7050-10	$189.99		
						Yes	20	PE7050-20	$189.99		
						Yes	30	PE7050-30	$157.99		
				Tri-Metal Plated Brass			1	PE7438-1	$92.99		49
							2	PE7438-2	$92.99		
							3	PE7438-3	$92.99		
							4	PE7438-4	$92.99		
							5	PE7438-5	$92.99		
							6	PE7438-6	$92.99		
							7	PE7438-7	$92.99		
							8	PE7438-8	$92.99		
							9	PE7438-9	$92.99		
							10	PE7438-10	$92.99		
							20	PE7438-20	$92.99		
	F Male	F Female	1,000 MHz	Nickel Plated Brass	1.3:1	Yes	1	PE7057-1	Call		50
						Yes	2	PE7057-2	$107.99		
						Yes	3	PE7057-3	$141.99		
						Yes	6	PE7057-6	$141.99		
						Yes	10	PE7057-10	$143.99		
			3 GHz	Tri-Metal Plated Brass			1	PE7396-1	$90.99		51
							2	PE7396-2	$92.99		
							3	PE7396-3	$86.99		
							4	PE7396-4	$111.99		
							5	PE7396-5	$105.99		
							6	PE7396-6	$85.99		
							7	PE7396-7	$111.99		
							8	PE7396-8	$111.99		
							9	PE7396-9	$103.99		
							10	PE7396-10	$103.99		
							16	PE7396-16	$111.99		
							20	PE7396-20	$78.99		
	N Male	N Female	4 GHz	Passivated Stainless Steel		Yes	1	PE7044-1	$197.99		52

See Our Website For Current Pricing & Real-Time Stock Availability!

* Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.

Fixed Attenuators

75 Ohm



Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1-9	10-24	25-49	50+	ROW
2 W	N Male	N Female	4 GHz	Passivated Stainless Steel	1.3:1	Yes	2	PE7044-2	$197.99	$188.09	$178.19	$170.27	52
						Yes	3	PE7044-3	$193.99	$184.29	$174.59	$166.83	
						Yes	6	PE7044-6	$221.99	$213.11	$206.45	$202.01	
						Yes	10	PE7044-10	$193.99	$184.29	$174.59	$166.83	
						Yes	20	PE7044-20	$193.99	$184.29	$174.59	$166.83	
						Yes	30	PE7044-30	$193.99	$184.29	$174.59	$166.83	

Step Attenuators, Push Button

50 Ohm



Max. Power (Watts)	Conn. Input	Conn. Output	Frequency Range (MHz)	Construction Material	VSWR Max. (MHz)	ATTN. Range (dB)	Step Size (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
1 W	BNC Female	BNC Female	DC-750	Brass	DC-100: 1.1:1 100-300: 1.25:1 300-500: 1.25:1 500-750: 1.4:1	0-65	1.0	PE7008-1	$1,090.00		See Web for Volume Pricing		53
					1.4:1	0-82.5		PE70A1021	$1,730.00				54
					DC-100: 1.1:1 100-300: 1.25:1 300-500: 1.25:1 500-750: 1.4:1	0-45.5	0.5	PE7008-2	$1,190.00				55
					1.4:1	0-102	1.0	PE7008-5	$1,500.00				
						0-82.5	0.5	PE7008-6	$1,380.00				

75 Ohm



Max. Power (Watts)	Conn. Input	Conn. Output	Frequency Range (MHz)	Construction Material	VSWR Max. (MHz)	ATTN. Range (dB)	Step Size (dB)	Model No	1-4	5-9	10-24	25+	ROW
1 W	BNC Female	BNC Female	DC-500	Brass	DC-100: 1.1:1 100-300: 1.2:1 300-500: 1.3:1	0-65	1.0	PE7008-3	$1,100.00	$1,045.00	$990.00	$946.00	55

Step Attenuators, Toggle

75 Ohm



Max. Power (Watts)	Conn. Input	Conn. Output	Frequency Range (MHz)	Construction Material	VSWR Max. (MHz)	ATTN. Range (dB)	Step Size (dB)	Model No	1-4	5-9	10-24	25+	ROW
1 W	BNC Female	BNC Female	DC-1,000	Aluminum	1.3:1	0-42		PE70A1001	$860.00	$817.00	$774.00	$739.60	56
	F Female	F Female	0.3-1,000		1.37:1	0-71		PE70A1008	$940.00	$893.00	$846.00	$808.40	57

See Our Website For Current Pricing & Real-Time Stock Availability!

Step Attenuators, Rotary

50 Ohm




Max. Power (Watts)	Conn. Input	Conn. Output	Frequency Range (MHz)	Construction Material	VSWR Max. (MHz)	ATTN. Range (dB)	Step Size (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
1 W	BNC Female	BNC Female	DC-1,000	Aluminum	1.2:1	0-1	0.1	PE7034-1	$740.00	See Web for Volume Pricing	58
					DC-1,000: 1.2:1	0-100	10.0	PE7034-2	$880.00		
2 W	BNC Female	BNC Female	DC-2,000	Aluminum	1.3:1	0-1	0.1	PE7034-6	$775.00		58
			DC-2,200		DC-1,000: 1.2:1 1,000-2,200: 1.4:1	0-10	1.0	PE70A1024	$765.00		59
						0-70	10.0	PE70A1022	$1,010.00		60
	SMA Female	SMA Female	DC-2,200	Aluminum	DC-1,000: 1.2:1 1,000-2,200: 1.4:1	0-10	1.0	PE70A1025	$725.00		61
						0-70	10.0	PE70A1023	$785.00		62

75 Ohm



Max. Power (Watts)	Conn. Input	Conn. Output	Frequency Range (MHz)	Construction Material	VSWR Max. (MHz)	ATTN. Range (dB)	Step Size (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
1 W	BNC Female	BNC Female	DC-500	Aluminum	1.3:1	0-10	1.0	PE7035-2	$510.00	See Web for Volume Pricing	63
			DC-1,000		DC-500: 1.3:1 500-1,000: 1.4:1	0-1	0.1	PE7035-5	$1,160.00		

DC Bias Attenuators

50 Ohm





Max. Power (Watts)	Conn. Input	Conn. Output	Frequency Range (MHz)	Construction Material	VSWR Max.	Max. V (V)	Max. I (Amp)	ATTN. (dB)	Model No	1-9	10-24	25-49	50+	ROW
2 W	N Male	N Female	500-2,000	Passivated Stainless Steel	1.35:1	100	2	6	PE7062-6	$201.99	$191.89	$181.79	$173.71	64
								10	PE7062-10	$197.99	$188.09	$178.19	$170.27	
								20	PE7062-20	$169.99	$161.49	$152.99	$146.19	
	SMA Male	SMA Female						6	PE7061-6	$167.99	$159.59	$151.19	$144.47	65
								10	PE7061-10	$179.99	$170.99	$161.99	$154.79	
								20	PE7061-20	$205.99	$195.69	$185.39	$177.15	
	TNC Male	TNC Female						6	PE7063-6	$183.99	$174.79	$165.59	$158.23	66
								10	PE7063-10	$231.99	$220.39	$208.79	$199.51	
								20	PE7063-20	$249.99	$237.49	$224.99	$214.99	

See Our Website For Current Pricing & Real-Time Stock Availability!

DC Bias Attenuators

75 Ohm



Max. Power (Watts)	Conn. Input	Conn. Output	Frequency Range (MHz)	Construction Material	VSWR Max.	Max. V (V)	Max. I (Amp)	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
2 W	F Male	F Female	500-2,000	Brass	1.45:1	100	2	6	PE7064-6	$215.99		See Web for Volume Pricing		67
								10	PE7064-10	$215.99				

Continuously Variable Attenuators

50 Ohm



Max. Power (Watts)	Conn. Input	Conn. Output	Frequency Range (MHz)	Construction Material	VSWR Max.	ATTN. (dB)	Model No	1	2-4	5-9	10+	ROW
5 W	SMA Female	SMA Female	DC-4,000		DC-1,000: 1.5:1 1,000-2,000: 1.6:1 2,000-3,000: 1.7:1 3,000-4,000: 1.8:1	5-95	PE7422	$1,900.00	$1,824.00	$1,748.00	$1,672.00	68

ACTIVE ATTENUATORS

TTL, USB, CMOS and Relay






Type	Frequency Range (GHz)	Atten. Range (dB)	IL (dB)	Step Resolu-tion (dB)	Switching Speed (µs)	Input/Output Connector	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
CMOS	DC - 13	0 - 31.5	5	0.5		SMA Female	PE70A5003	$5,520.00		See Web for Volume Pricing		69
Relay	DC - 1		1.5		6,000,000		PE70A8001	$1,030.00				70
	DC - 1	0 - 63	1.5	1			PE70A8000	$1,090.00				71
	DC - 1		2.2			F Female	PE70A8003	$2,000.00				72
	DC - 1	0 - 127	2.5				PE70A8004	$2,380.00				73
	DC - 1.5		3.2			SMA Female	PE70A8005	$2,590.00				74
	DC - 2	0 - 63.75		0.25			PE70A8002	$3,540.00				75
	DC - 2.5	0 - 63	2	1	6,000		PE70A8013	$4,030.00				76
	DC - 2.7		3.5		10,000,000		PE70A8014	$4,990.00				77
	100 MHz - 18		4		350		PE70A8007	$4,100.00				78
	100 MHz - 18		4				PE70A8012	$4,270.00				79

See Our Website For Current Pricing & Real-Time Stock Availability!

TTL, USB, CMOS and Relay






Type	Frequency Range (GHz)	Atten. Range (dB)	IL (dB)	Step Resolution (dB)	Switching Speed (µs)	Input/Output Connector	Model No	1	2-4	5-9	10+	ROW
TTL	DC - 13	0 - 31.5	5.5	0.5	45		PE70A4000	$5,940.00	$5,702.40	$5,464.80	$5,227.20	85
	5 MHz - 2.15	0 - 63	5.25	1	5,000	F Female	PE70A5012	$2,360.00	$2,265.60	$2,171.20	$2,076.80	86
	30 MHz - 3	0 - 31.75	2.5	0.25	1,000	SMA Female	PE70A5004	$1,880.00	$1,804.80	$1,729.60	$1,654.40	87
	30 MHz - 3	0 - 63	4	1			PE70A5006	$1,860.00	$1,785.60	$1,711.20	$1,636.80	88
	30 MHz - 3	0 - 63.5	4	0.5			PE70A5005	$1,810.00	$1,737.60	$1,665.20	$1,592.80	89
	30 MHz - 3	0 - 95	6	1			PE70A5007	$2,410.00	$2,313.60	$2,217.20	$2,120.80	90
	30 MHz - 6	0 - 60	4	0.25	50,000		PE70A5000	$7,230.00	$6,940.80	$6,651.60	$6,362.40	91
	100 MHz - 18	0 - 30	5	1	1	2.92mm Female	PE70A5001	$8,440.00	$8,102.40	$7,764.80	$7,427.20	92
	100 MHz - 40		8				PE70A5002	$12,300.00	$11,808.00	$11,316.00	$10,824.00	93
	200 MHz - 6	0 - 63	5.5	1	1,000	SMA Female	PE70A5009	$1,880.00	$1,804.80	$1,729.60	$1,654.40	94
	200 MHz - 6	0 - 95	8				PE70A5010	$2,290.00	$2,198.40	$2,106.80	$2,015.20	95
	450 MHz - 2.15	0 - 127	4.5		2,000	F Female	PE70A5011	$2,390.00	$2,294.40	$2,198.80	$2,103.20	96
	500 MHz - 18	0 - 60	4.5	0.06	1	SMA Female	PE70A6000	$8,270.00	$7,939.20	$7,608.40	$7,277.60	97
	700 MHz - 3	0 - 127	6	1	5,000		PE70A5008	$2,320.00	$2,227.20	$2,134.40	$2,041.60	98
	18 - 40	0 - 30		0.03	1	2.4mm Female	PE70A6001	$9,070.00	$8,707.20	$8,344.40	$7,981.60	99
Bench-Top TTL	200 MHz - 6	0 - 95	8	1	1,000	SMA Female	PE70A5013	$11,225.00	$10,776.00	$10,327.00	$9,878.00	1
USB	100 MHz - 18	0 - 30	5				PE70A3900	$5,020.00	$4,819.20	$4,618.40	$4,417.60	2
	100 MHz - 40					2.92mm Female	PE70A3901	$6,820.00	$6,547.20	$6,274.40	$6,001.60	3
	200 MHz - 6	0 - 95	8.3		4,000	SMA Female	PE70A3902	$2,440.00	$2,342.40	$2,244.80	$2,147.20	4

Variable Voltage Attenuators






Frequency Range (GHz)	Atten. Range (dB)	Insertion Loss (dB)	Switching Speed (µsec)	Input / Output Connectors	Model No	1	2-4	5-9	10+	ROW
DC - 20	0 - 30			SMA Female	PE70A1017	$10,425.00	$10,008.00	$9,591.00	$9,174.00	5
50 MHz - 2.2	0 - 20	3	50,000		PE70A1031	$1,700.00	$1,632.00	$1,564.00	$1,496.00	6
500 MHz - 18	0 - 60	4.5	3,000		PE70A2900	$7,930.00	$7,612.80	$7,295.60	$6,978.40	8
2 - 4		2	500		PE70A2000	$6,780.00	$6,508.80	$6,237.60	$5,966.40	9
4 - 8		2.5			PE70A2001	$7,950.00	$7,632.00	$7,314.00	$6,996.00	10
6 - 12		2.8			PE70A2002	$8,340.00	$8,006.40	$7,672.80	$7,339.20	11
8 - 18		3.7			PE70A2003	$8,730.00	$8,380.80	$8,031.60	$7,682.40	12

EQUALIZERS

Positive Slope



Frequency Range (GHz)	Typ. Equalizing Value (dB)	Typ. Small Signal IL (dB)	Typ Input-Output VSWR	Max. RF Input Power (dBm)	In-Out Connectors (Field Replaceable)	Model No	1-4	5-9	10-24	24+	ROW
0.5 - 2	2	1.4	1.8:1	+30	SMA Female	PE70A9000	$825.00	$783.75	$742.50	$709.50	13
	4	1				PE70A9001	$845.00	$802.75	$760.50	$726.70	14
	6	1.8				PE70A9002	$860.00	$817.00	$774.00	$739.60	15
1 - 18	4	1				PE70A9003	$1,470.00	$1,396.50	$1,323.00	$1,264.20	16

See Our Website For Current Pricing & Real-Time Stock Availability!

Positive Slope




Frequency Range (GHz)	Typ. Equal-izing Value (dB)	Typ. Small Signal IL (dB)	Typ Input-Output VSWR	Max. RF Input Power (dBm)	In-Out Con-nectors (Field Replaceable)	Model No	1-4	5-9	10-24	25+	ROW
1 - 18	6	1	1.8:1	+30	SMA Female	PE70A9004	$1,470.00	$1,396.50	$1,323.00	$1,264.20	17
	8	1.5				PE70A9005	$1,470.00	$1,396.50	$1,323.00	$1,264.20	18
2 - 6	2	1				PE70A9006	$1,180.00	$1,121.00	$1,062.00	$1,014.80	19
	4	1.5				PE70A9007	$1,230.00	$1,168.50	$1,107.00	$1,057.80	20
2 - 12		1.5				PE70A9008	$1,180.00	$1,121.00	$1,062.00	$1,014.80	21
	8	1.5				PE70A9009	$1,280.00	$1,216.00	$1,152.00	$1,100.80	22
6 - 18	2	1.5				PE70A9010	$1,410.00	$1,339.50	$1,269.00	$1,212.60	23
	4	1.5				PE70A9011	$1,440.00	$1,368.00	$1,296.00	$1,238.40	24
	6	2				PE70A9012	$1,470.00	$1,396.50	$1,323.00	$1,264.20	25
	8	1.5				PE70A9013	$1,510.00	$1,434.50	$1,359.00	$1,298.60	26
18 - 40	2	2			2.92mm Female	PE70A9014	$1,650.00	$1,567.50	$1,485.00	$1,419.00	27
	4	2				PE70A9015	$1,690.00	$1,605.50	$1,521.00	$1,453.40	28
	6	2				PE70A9016	$1,720.00	$1,634.00	$1,548.00	$1,479.20	29
26.5 - 40	4	3				PE70A9017	$1,650.00	$1,567.50	$1,485.00	$1,419.00	30
	5	2.5				PE70A9018	$1,680.00	$1,596.00	$1,512.00	$1,444.80	31

BALUNS



Frequency Range (MHz)	Balanced Impedance (Ω)	Unbalanced Impedance (Ω)	Package	Model No	1-9	10-24	25-49	50+	ROW
20 - 520	25	50	Surface Mount	PE2BL1001	$307.99	$292.59	$277.19	$264.87	32
20 - 1,000				PE2BL1002	$297.99	$283.09	$268.19	$256.27	33
80 - 1,000				PE2BL1003	$273.99	$260.29	$246.59	$235.63	34
100 - 520				PE2BL1004	$297.99	$283.09	$268.19	$256.27	35
225 - 2,000				PE2BL1000	$289.99	$275.49	$260.99	$249.39	36

BIAS TEES





Impedance	Frequency Range (MHz.)	Max. V (V)	Max. I (mA)	Connector	Bias Connector	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
50 Ohm	0.03 - 70,000	100	2500	1.85mm	SMA	PE1619	$3,840.00	See Web for Volume Pricing	39
	0.03 - 85,000					PE1620	$3,750.00		40
	0.05 - 50,000	25	250	2.4mm		PE1610	$2,260.00		41
	0.1 - 12,400	100	2500	SMA	Solder Pin	PE1606A	$785.00		42
	0.1 - 18,000					PE1BT1002	$865.00		43
	0.1 - 26,500	24	750	3.5mm		PE1608	$1,510.00		44
	10 - 2,500	100	2500	SMA	Solder Pin	PE1611	$515.00		45
	10 - 4,000					PE1613	$565.00		46
				N		PE1614	$520.00		47
	10 - 6,000					PE1612	$477.99		48
				SMA		PE1615	$467.99		49
				N		PE1616	$605.00		50
	10 - 40,000			2.92mm	Pin	PE1621	$1,520.00		51
	100 - 6,000	50	500	SMA	Solder Pin	PE1604	$393.99		52
	250 - 2,500	100	7000			PE1617	$835.00		53
				N		PE1618	$1,030.00		54
	400 - 10,000	50	200	SMA		PE1605	$610.00		55
	500 - 10,000				Pin	PE1BT1000	$1,210.00		56
	500 - 40,000			2.92mm		PE1622	$1,690.00		57
	1,000 - 5,000	50	1000	SMA	Solder Pin	PE1603	$391.99		58

See Our Website For Current Pricing & Real-Time Stock Availability!

DC BLOCKS







Impedance	Connector	Frequency Range (MHz.)	Type	Max. V (V)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
50 Ohm	1.85mm	10 - 65,000	Inner	16	PE8258	$830.00	See Web for Volume Pricing	59
	2.4mm	100 - 50,000	Inner	75	PE8237	$1,740.00		60
			Inner/Outer		PE8239	$2,110.00		61
		10 - 50,000	Inner	50	PE8268	$530.00		62
	2.92mm	10 - 26,500	Inner	200	PE8222	$343.99		63
			Inner/Outer		PE8224	$625.00		65
		10 - 40,000	Inner		PE8225	$855.00		66
			Inner/Outer		PE8227	$1,470.00		68
			Inner	50	PE8267	$253.99		69
	BNC	10 - 4,000	Inner	200	PE8216	$231.99		70
			Outer		PE8217	$377.99		71
			Inner/Outer		PE8218	$377.99		72
			Inner		PE8263	$79.99		73
		10 - 3,000	Inner	100	PE8270	$42.59		74
		30 - 1,000	Inner	500	PE8274	$76.99		75
			Inner		PE8275	$101.99		76
		10 - 3,000	Inner	100	PE8282	$47.79		77
	MCX	10 - 6,000	Inner	50	PE8269	$63.99		78
	N	10 - 18,000	Inner	200	PE8213	$177.99		79
			Outer		PE8214	$261.99		80
			Inner/Outer		PE8215	$319.99		81
			Inner	950	PE8251	$237.99		82
		50 - 18,000	Inner	200	PE8265	$105.99		83
		10 - 5,000	Inner	100	PE8271	$79.99		84
		30 - 1,000	Inner	1000	PE8276	$127.99		85
		10 - 3,000	Inner	100	PE8280	$79.99		86
			Inner		PE8281	$79.99		87
	SMA	10 - 18,000	Inner	200	PE8210	$131.99		88
			Outer		PE8211	$257.99		89
			Inner/Outer		PE8212	$299.99		90
			Inner	950	PE8250	$193.99		91
			Inner	200	PE8266	$54.99		92
		10 - 18,500	Inner		PE8273	$42.59		93
		10 - 5,000	Inner	100	PE8277	$79.99		94
		10 - 3,000	Inner		PE8278	$47.79		95
			Inner		PE8279	$47.79		96
	TNC	10 - 18,000	Inner	200	PE8219	$281.99		97
			Outer		PE8220	$391.99		98
			Inner/Outer		PE8221	$471.99		99
		50 - 18,000	Inner		PE8264	$95.99		2
		10 - 3,000	Inner	100	PE8272	$42.59		3
75 Ohm	BNC	100 - 4,000	Inner	200	PE8231	$367.99		4
			Inner/Outer		PE8233	$439.99		6
		10 - 3,000	Inner		PE8261	$74.99		7
	F	10 - 2,000	Inner		PE8240	$185.99		8
			Inner/Outer		PE8242	$321.99		9
		10 - 3,000	Inner		PE8260	$68.99		10
	N		Inner		PE8262	$121.99		13

See Our Website For Current Pricing & Real-Time Stock Availability!

The Cable Creator™

Configure and Customize Your Cable Assemblies Online



Over 250,000 Custom Cable Configurations Available to Ship Same Day!



- Choose from over 2,030 RF coax connectors
- 123 coaxial cable types, including Twinax
- Choose your desired length (metric or standard)
- Includes high-reliability and low PIM assembly types
- ISO 9001:2015 certified production facility
- Optional Customizations:
  - Lead-free solder
  - Heat shrink
  - Labeling
  - Test plots
  - Clocking of right angle connectors

Create your custom cable today

www.pasternack.com/t-cable-creator.aspx

PASTERNACK
an INFINITE brand

Our Latest Cable Assembly Additions

Available in Standard and Custom Lengths! In-Stock and Shipped Same Day



High-Reliability Cable Assemblies

- MIL-DTL-17 and Temperature Conditioned, Low Loss Options
- Maximum Frequency Levels as High as 18 GHz
- J-STD Soldering Processes
- IPC/WHMA-A-620 Workmanship
- Lot Traceability for Cables, Connectors, Heat Shrink and Solder
- Detailed Test Reports and Plots

Low PIM Cable Assemblies

- Maximum PIM Levels as Low as -160dBc
- 100% PIM Tested with Results Marked on the Cable
- Low Loss, Excellent VSWR
- Lightweight, Extremely Flexible
- UL-Rated, Fire-Rated, Outdoor-Rated Cable Types
- Available with 4.3-10, 7/16 DIN, 4.1/9.5 Mini-DIN, Type-N, NEX10, SMA, and QMA Connector Series





40 GHz and 67 GHz Skew Matched Cable Pairs

- 1 ps Delay Match
- Excellent VSWR of 1.4:1
- 100% Tested Up to 40 or 67 GHz
- Extremely Flexible
- Polarity Indicators on Cable Ends

Handheld RF Analyzer Rugged Phase Stable Cable Assemblies

- VSWR as Low as 1.2:1
- Phase Stability with Flexure as Low as ± 1.5 Degrees
- Amplitude Stability with Flexure as Low as ± 0.1 dB
- Rugged Armor with 1200 PSI Crush Resistance, Protects Cable During Field Measurements
- UV Resistant Jacket
- Test Data Included with Each Serialized Cable





PE-P160LL Low Loss Cable Assemblies

- Triple-Shielded Low Loss Cable
- Maximum Frequency Levels as High as 18 GHz
- Shielding Effectivity >90 dB
- FEP Jacket
- 83% Phase Velocity
- Available with Type-N, SMA, and TNC Connector Series with Bulkhead and Right Angle Options

Coaxial Cable Assemblies Selection Guide

Do you need a cable assembly that isn't in our RF Product Guide?
Visit our website to view our entire selection of available assemblies or to build your own custom length cable assembly!

3 Easy Ways to Find your Product.....

1. Search by PE Part Number

If you know the PE part number you are searching for, please reference our Part Number Index on Page 404

2. Quick Reference Guide

(Page number refers to first appearance of product in the Cable Assemblies Section)

Cable Connector	Page
1.0/2.3	104
1.0mm	104
1.85mm	104
2.2-5	105
2.4mm	107
2.4mm NMD	107
2.92mm	107
2.92mm NMD	108
3.5mm	109
3.5mm NMD	109
4.1/9.5 Mini DIN	112
4.3-10	117
6G SDI 75 Ohm 1.0/2.3	218
6G SDI 75 Ohm BNC	219

Cable Connector	Page
6G SDI 75 Ohm HD-BNC	220
7/16 DIN	123
10-32	124
12G SDI 75 Ohm 1.0/2.3	218
12G SDI 75 Ohm BNC	218
12G SDI 75 Ohm HD-BNC	220
75 Ohm 1.6/5.6	218
75 Ohm BNC	220
75 Ohm F	221
75 Ohm Mini SMB	221
75 Ohm N	222
75 Ohm SMB	222
75 Ohm SMC	223

Cable Connector	Page
75 Ohm TNC	223
78 Ohm BNC Twinax	223
95 Ohm 3/4"-20 Twinax	223
Banana	223
BMA	127
BNC	134
C	135
D-Sub	135
FAKRA	137
FME	139
GR874	139
HMCX32 1.2	217
HN	139
LC	140

Cable Connector	Page
MC-Card	140
MCX	141
MHV	142
Mini UHF	143
MMBX	144
MMCX	143
N	162
NEX10	165
NMO Mount	165
QMA	166
QN	167
Reverse Polarity SMA	200
Reverse Polarity TNC	215
Reverse Thread SMA	200

Cable Connector	Page
SC	167
SHV	168
SMA	194
SMB	201
SMC	206
SMP	207
SSMA	208
SSMB	208
SSMC	210
TNC	215
UHF	216
UMCX 2.1	218
UMCX 2.5	218
UMCX	217
WMCX 1.6	218

3. Cable Assembly Locator

(Cable Assembly Locator on Page 95-98 to locate the Cable Assembly you need by either connector end.)



SMA Female Bulkhead to MCX Plug Right Angle
PE39421-12

SMA FEMALE BULKHEAD TO:	EXAMPLE
MCX PLUG RIGHT ANGLE	23
MMCX PLUG RIGHT ANGLE	23
SMA FEMALE BULKHEAD	43
SMA MALE	17,23,31,32
SMA MALE RIGHT ANGLE	17,23,40,41
UMCX PLUG	76

MCX PLUG RIGHT ANGLE TO:	EXAMPLE
MCX PLUG	78
MCX PLUG RIGHT ANGLE	79
N FEMALE BULKHEAD	25
SMA FEMALE BULKHEAD	23
TNC FEMALE BULKHEAD	27
UMCX PLUG	76

The Cable Assembly Locator example above includes Between-Series Cable Assembly part numbers in two configurations: ***Connector 1 to Connector 2 as well as Connector 2 to Connector 1 will be found in the same location.***

Products can only be found under the first instance of the series combination. As an example, PE39421-12 above will be found in only one location in the Cable Assembly Section.

All Pasternack coaxial cable assembly part number indicate the length of the assembly (in inches) following the hyphen. Example: PE300-24 and PE300-26.5 are 24 inches and 26.5 inches in length respectively

NOTE: All cable assemblies have a length tolerance of 1.5% or ± 3/8", whichever is greater.

Cable Assembly Locator

Connector Type	Page
1.0/2.3 Jack Bulkhead To:	
1.0/2.3 JACK BULKHEAD	104
1.0/2.3 Plug To:	
BNC FEMALE BULKHEAD	104
1.0/2.3 Plug Right Angle To:	
BNC MALE	104
1.0mm Male To:	
1.0mm FEMALE	104
1.0mm MALE	104
1.85mm Male To:	
1.85mm FEMALE	104
1.85mm MALE	104
1.85mm MALE RIGHT ANGLE	104
2.4mm MALE	104
2.92mm MALE	105
2.2-5 Female To:	
4.3-10 MALE RIGHT ANGLE	105
N FEMALE	106
N FEMALE BULKHEAD	106
N MALE	105
N MALE RIGHT ANGLE	106
2.2-5 Male To:	
2.2-5 FEMALE	105
2.2-5 FEMALE BULKHEAD	105
2.2-5 MALE RIGHT ANGLE	105
N FEMALE	105
N FEMALE BULKHEAD	105
N MALE RIGHT ANGLE	105
2.2-5 Male Right Angle To:	
2.2-5 FEMALE	105
2.2-5 FEMALE BULKHEAD	105
2.2-5 MALE RIGHT ANGLE	105
2.4mm Female Bulkhead To:	
SMA MALE	107
2.4mm Male To:	
1.85mm MALE	106
2.4mm FEMALE	106
2.4mm MALE	106
2.4mm MALE RIGHT ANGLE	106
2.92mm MALE	106
SMA MALE	106
2.4mm NMD Female To:	
2.4mm FEMALE	107
2.4mm MALE	107
2.92mm Male To:	
1.85mm MALE	107
2.4mm MALE	107
2.92mm FEMALE	107
2.92mm FEMALE BULKHEAD	108
2.92mm MALE	107
2.92mm NMD Female To:	
2.92mm FEMALE	108
2.92mm MALE	108
3.5mm Female To:	
2.92mm MALE	109
3.5mm FEMALE	109
3.5mm NMD FEMALE	109
3.5mm Male To:	
1.85mm MALE	108
3.5mm FEMALE	108
3.5mm FEMALE BULKHEAD	109
3.5mm MALE	108
3.5mm NMD Female To:	
3.5mm MALE	109
4.1/9.5 Mini DIN Female To:	
4.3-10 MALE	112
4.3-10 MALE RIGHT ANGLE	112
7/16 DIN MALE	112
7/16 DIN MALE RIGHT ANGLE	112
N MALE RIGHT ANGLE	112
4.1/9.5 Mini DIN Male To:	
4.1/9.5 MINI DIN FEMALE	109
4.1/9.5 MINI DIN FEMALE BULKHEAD	109
4.1/9.5 MINI DIN MALE	109
4.1/9.5 MINI DIN MALE RIGHT ANGLE	109
4.3-10 FEMALE	110
4.3-10 FEMALE BULKHEAD	110
4.3-10 MALE	109
4.3-10 MALE RIGHT ANGLE	110
7/16 DIN FEMALE	110
7/16 DIN FEMALE 4 HOLE FLANGE	110
7/16 DIN MALE	110
7/16 DIN MALE RIGHT ANGLE	110
N FEMALE	110
N FEMALE BULKHEAD	111
N MALE	110
N MALE RIGHT ANGLE	110
QMA FEMALE	111
QMA MALE	111
QMA MALE RIGHT ANGLE	111
SMA FEMALE	111
SMA MALE	111
SMA MALE RIGHT ANGLE	111
4.1/9.5 Mini DIN Male Right Angle To:	
4.1/9.5 MINI DIN FEMALE	111
4.1/9.5 MINI DIN FEMALE BULKHEAD	111
4.1/9.5 MINI DIN MALE RIGHT ANGLE	111
4.3-10 FEMALE	111
4.3-10 MALE	111
7/16 DIN MALE	112
N MALE	112
N MALE RIGHT ANGLE	112
QMA MALE	112
SMA MALE	112
4.3-10 Female To:	
4.3-10 MALE	117
7/16 DIN MALE	117
7/16 DIN MALE RIGHT ANGLE	117
N MALE	117
N MALE RIGHT ANGLE	117
NEX10 MALE	118
4.3-10 Female Bulkhead To:	
7/16 DIN MALE	118
7/16 DIN MALE RIGHT ANGLE	118
N MALE	118
N MALE RIGHT ANGLE	118
4.3-10 Male To:	
4.3-10 FEMALE	113
4.3-10 FEMALE 4 HOLE FLANGE	113
4.3-10 FEMALE BULKHEAD	113
4.3-10 MALE	112
4.3-10 MALE RIGHT ANGLE	113
7/16 DIN FEMALE	113
7/16 DIN FEMALE 4 HOLE FLANGE	114
7/16 DIN MALE	113
7/16 DIN MALE RIGHT ANGLE	113
N FEMALE	114
N FEMALE BULKHEAD	114
N MALE	114
N MALE RIGHT ANGLE	114
NEX10 MALE	115
QMA FEMALE	115
QMA MALE	114
QMA MALE RIGHT ANGLE	114
SMA FEMALE	115
SMA MALE	115
SMA MALE RIGHT ANGLE	115
4.3-10 Male Right Angle To:	
4.3-10 FEMALE	115
4.3-10 FEMALE 4 HOLE FLANGE	116
4.3-10 FEMALE BULKHEAD	116
4.3-10 MALE	115
4.3-10 MALE RIGHT ANGLE	115
7/16 DIN FEMALE	116
7/16 DIN FEMALE 4 HOLE FLANGE	116
7/16 DIN MALE	116
7/16 DIN MALE RIGHT ANGLE	116
N FEMALE	117
N FEMALE BULKHEAD	117
N MALE	116
N MALE RIGHT ANGLE	116
NEX10 MALE	117
SMA MALE	117
SMA MALE RIGHT ANGLE	117
6G SDI 75 Ohm 1.0/2.3 Male To:	
75 Ohm 1.0/2.3 MALE	218
6G SDI 75 Ohm BNC Male To:	
75 Ohm 1.0/2.3 MALE	219
75 Ohm BNC MALE	219
75 Ohm HD-BNC MALE	219
6G SDI 75 Ohm HD-BNC Male To:	
75 Ohm 1.0/2.3 MALE	220
75 Ohm HD-BNC MALE	220
7/16 DIN Female To:	
7/16 DIN FEMALE	123
N FEMALE	124
N MALE	123
N MALE RIGHT ANGLE	123
NEX10 MALE	124
7/16 DIN Male To:	
4.3-10 FEMALE	118
7/16 DIN FEMALE	119
7/16 DIN FEMALE 4 HOLE FLANGE	120
7/16 DIN FEMALE BULKHEAD	120
7/16 DIN MALE	118
7/16 DIN MALE RIGHT ANGLE	119
N FEMALE	121
N FEMALE BULKHEAD	121
N MALE	120
N MALE RIGHT ANGLE	120
QMA FEMALE	121
QMA MALE	121
QMA MALE RIGHT ANGLE	121
SC MALE	121
SMA FEMALE	122
SMA MALE	121
SMA MALE RIGHT ANGLE	122
7/16 DIN Male Right Angle To:	
7/16 DIN FEMALE	122
7/16 DIN FEMALE 4 HOLE FLANGE	122
7/16 DIN FEMALE BULKHEAD	122
7/16 DIN MALE	122
7/16 DIN MALE RIGHT ANGLE	122
N FEMALE	123
N FEMALE BULKHEAD	123
N MALE	122
N MALE RIGHT ANGLE	123
NEX10 MALE	123
10-32 Female To:	
BNC MALE	124
10-32 Male To:	
10-32 MALE	124
10-32 MALE RIGHT ANGLE	124
BNC MALE	124
10-32 Male Right Angle To:	
10-32 MALE RIGHT ANGLE	124
SMP FEMALE	124
12G SDI 75 Ohm 1.0/2.3 Male To:	
75 Ohm 1.0/2.3 MALE	218
12G SDI 75 Ohm BNC Male To:	
75 Ohm 1.0/2.3 MALE	218
75 Ohm BNC MALE	219
75 Ohm HD-BNC MALE	219
12G SDI 75 Ohm HD-BNC Male To:	
75 Ohm 1.0/2.3 MALE	220
75 Ohm HD-BNC MALE	220

Cable Assembly Locator

Connector Type	Page
75 Ohm 1.6/5.6 Plug To:	
75 Ohm 1.6/5.6 PLUG	218
75 Ohm 1.6/5.6 PLUG RIGHT ANGLE	218
75 Ohm BNC MALE	218
75 Ohm 1.6/5.6 Plug Right Angle To:	
75 Ohm 1.6/5.6 PLUG RIGHT ANGLE	218
75 Ohm BNC Female To:	
75 Ohm BNC FEMALE	220
75 Ohm BNC Female Bulkhead To:	
75 Ohm BNC FEMALE BULKHEAD	220
75 Ohm BNC Male To:	
75 Ohm BNC FEMALE	219
75 Ohm BNC FEMALE BULKHEAD	219
75 Ohm BNC MALE	219
75 Ohm BNC MALE RIGHT ANGLE	219
75 Ohm BNC Male Right Angle To:	
75 Ohm BNC MALE RIGHT ANGLE	220
75 Ohm F Female To:	
75 Ohm F FEMALE	221
75 Ohm F Male To:	
75 Ohm BNC MALE	220
75 Ohm F FEMALE	221
75 Ohm F FEMALE BULKHEAD	221
75 Ohm F MALE	221
75 Ohm F MALE RIGHT ANGLE	221
75 Ohm Mini SMB Plug To:	
75 Ohm BNC MALE	221
75 Ohm MINI SMB PLUG	221
75 Ohm MINI SMB PLUG RIGHT ANGLE	221
75 Ohm Mini SMB Plug Right Angle To:	
75 Ohm F FEMALE BULKHEAD	221
75 Ohm MINI SMB PLUG RIGHT ANGLE	221
75 Ohm N Female To:	
75 Ohm N FEMALE	222
75 Ohm N Male To:	
75 Ohm BNC MALE	222
75 Ohm F FEMALE	222
75 Ohm F MALE	222
75 Ohm N FEMALE	222
75 Ohm N MALE	222
75 Ohm SMB Plug To:	
75 Ohm BNC MALE	222
75 Ohm SMB PLUG	222
75 Ohm SMC Plug To:	
75 Ohm BNC MALE	223
75 Ohm SMC PLUG	223
75 Ohm TNC Male To:	
75 Ohm BNC MALE	223
75 Ohm TNC MALE	223
78 Ohm BNC Twinax Plug To:	
78 Ohm BNC TWINAX PLUG	223
95 Ohm 3/4"-20 Twinax Male To:	
95 Ohm 3/4"-20 TWINAX MALE	223
Banana Plug To:	
SMA MALE	223
BMA Jack To:	
BMA JACK	127
BNC MALE	127
N MALE	127
SMA MALE	127
SMA MALE RIGHT ANGLE	127
SMP FEMALE	128
SMP FEMALE RIGHT ANGLE	128
TNC MALE	128
BMA Jack 2 Hole Flange To:	
BMA JACK 2 HOLE FLANGE	128
BNC MALE	128
N MALE	128
SMA MALE	129
SMA MALE RIGHT ANGLE	129
SMP FEMALE	129
SMP FEMALE RIGHT ANGLE	129
TNC MALE	129
BMA Jack Bulkhead To:	
BMA JACK BULKHEAD	128
BMA Jack Right Angle 2 Hole Flange To:	
BMA JACK RIGHT ANGLE 2 HOLE FLANGE	129
BMA Plug Bulkhead To:	
BMA JACK	125
BMA JACK 2 HOLE FLANGE	125
BMA JACK BULKHEAD	125
BMA JACK RIGHT ANGLE 2 HOLE FLANGE	125
BMA PLUG BULKHEAD	124
BNC MALE	125
N MALE	125
SMA MALE	126
SMA MALE RIGHT ANGLE	126
SMP FEMALE	126
SMP FEMALE RIGHT ANGLE	126
TNC MALE	126
BNC Female To:	
BNC FEMALE	134
BNC MALE RIGHT ANGLE	134
NMO Mount Sexless	135
BNC Female Bulkhead To:	
SMA MALE	135
BNC Male To:	
7/16 DIN FEMALE	129
BNC FEMALE	132
BNC FEMALE BULKHEAD	132
BNC MALE	130
BNC MALE RIGHT ANGLE	131
FAKRA PLUG	132
MHV MALE	133
N MALE	133
NMO Mount Sexless	129
SHV PLUG	133
SSMC JACK BULKHEAD	133
SSMC PLUG	133
SSMC PLUG RIGHT ANGLE	133
Straight Cut Lead Sexless	133
UHF FEMALE	133
BNC Male Right Angle To:	
BNC FEMALE BULKHEAD	134
BNC MALE RIGHT ANGLE	133
SMA FEMALE	134
TNC MALE RIGHT ANGLE	134
C Male To:	
C MALE	135
C Male Right Angle To:	
C MALE	135
D-Sub Receptacle To:	
BNC MALE	135
FAKRA Jack To:	
FAKRA JACK	137
FAKRA JACK RIGHT ANGLE	138
REVERSE POLARITY TNC MALE	138
SMA FEMALE	138
FAKRA Jack Right Angle To:	
FAKRA PLUG	138
FAKRA Plug To:	
FAKRA JACK	136
FAKRA JACK RIGHT ANGLE	137
FAKRA PLUG	135
SMA MALE	137
FME Jack To:	
BNC MALE	139
FME JACK	139
NMO Mount Sexless	139
FME Plug To:	
BNC MALE	138
FME PLUG	138
NMO Mount Sexless	138
FME Plug Bulkhead To:	
UMCX PLUG RIGHT ANGLE	138
GR874 Sexless To:	
BNC MALE	139
GR874 Sexless	139
HMCX32 1.2 Plug To:	
HMCX32 1.2 PLUG	217
HN Male To:	
7/16 DIN MALE RIGHT ANGLE	139
HN MALE	139
HN Male Right Angle To:	
HN FEMALE	140
LC Male To:	
LC MALE	140
LC Male Right Angle To:	
HN MALE	140
MC-Card Plug To:	
MC-Card PLUG	140
MC-Card PLUG RIGHT ANGLE	140
MC-Card Plug Right Angle To:	
MC-Card PLUG RIGHT ANGLE	140
MCX Jack To:	
MCX JACK	141
MCX Plug To:	
75 Ohm BNC MALE	140
BNC MALE	140
MCX PLUG	140
MCX PLUG RIGHT ANGLE	141
SMA MALE	141
TNC FEMALE BULKHEAD	141
MCX Plug Right Angle To:	
BNC FEMALE 4 HOLE FLANGE	141
MCX JACK BULKHEAD	141
MCX PLUG RIGHT ANGLE	141
SMA FEMALE	141
SMA MALE	141
MHV Male To:	
MHV MALE	142
MHV MALE RIGHT ANGLE	142
SHV PLUG	142
Mini UHF Female To:	
NMO Mount Sexless	143
Mini UHF Male To:	
MINI UHF MALE	143
NMO Mount Sexless	143
MMBX Plug To:	
MMBX PLUG	144
MMBX PLUG RIGHT ANGLE	144
N FEMALE BULKHEAD	144
REVERSE POLARITY SMA FEMALE BULKHEAD	145
SMA FEMALE	145
SMA FEMALE BULKHEAD	145
SMA MALE	144
SMA MALE RIGHT ANGLE	145
SSMB JACK BULKHEAD	145
TNC FEMALE BULKHEAD	145
MMBX Plug Right Angle To:	
MMBX PLUG RIGHT ANGLE	145
N FEMALE BULKHEAD	146
REVERSE POLARITY SMA FEMALE BULKHEAD	146
SMA FEMALE	146

Cable Assembly Locator

Connector Type	Page
MMBX Plug Right Angle To:	
SMA FEMALE BULKHEAD	146
SMA MALE	146
SMA MALE RIGHT ANGLE	146
TNC FEMALE BULKHEAD	147
MMCX Plug To:	
MMCX PLUG	143
MMCX PLUG RIGHT ANGLE	143
N FEMALE BULKHEAD	143
SMC PLUG	143
MMCX Plug Right Angle To:	
BNC FEMALE BULKHEAD	143
MMCX PLUG	144
N FEMALE BULKHEAD	144
SMA FEMALE	144
SMA FEMALE BULKHEAD	144
SMA MALE RIGHT ANGLE	144
N Female To:	
N FEMALE	162
N FEMALE BULKHEAD	162
N MALE	162
NMO Mount Sexless	162
QN MALE	162
QN MALE RIGHT ANGLE	163
SMA MALE	163
SMA MALE RIGHT ANGLE	163
TNC MALE	163
N Female 4 Hole Flange To:	
MMCX PLUG RIGHT ANGLE	165
N Female Bulkhead To:	
HMCX32 1.2 PLUG	164
MCX PLUG RIGHT ANGLE	163
MMCX PLUG RIGHT ANGLE	163
N FEMALE BULKHEAD	163
N MALE	163
N MALE RIGHT ANGLE	163
NEX10 MALE	165
QMA MALE RIGHT ANGLE	163
REVERSE POLARITY SMA MALE RIGHT ANGLE	164
SMA FEMALE	164
SMA FEMALE BULKHEAD	164
SMA MALE	164
SMA MALE RIGHT ANGLE	164
SMP FEMALE RIGHT ANGLE	164
TNC FEMALE BULKHEAD	164
TNC MALE	164
TNC MALE RIGHT ANGLE	164
UMCX 2.1 PLUG	164
UMCX 2.5 PLUG	164
WMCX 1.6 PLUG	165
N Male To:	
7/16 DIN FEMALE	147
7/16 DIN MALE	147
7/16 DIN MALE RIGHT ANGLE	147
BNC FEMALE BULKHEAD	148
BNC MALE	148
C FEMALE	148
GR874 Sexless	148
MCX PLUG RIGHT ANGLE	148
MINI UHF MALE	148
N FEMALE	153
N FEMALE 4 HOLE FLANGE	155
N FEMALE BULKHEAD	154
N MALE	149
N MALE RIGHT ANGLE	151
NEX10 MALE	159
NMO Mount Sexless	155
QMA MALE	155
QMA MALE RIGHT ANGLE	156
QN MALE	156
QN MALE RIGHT ANGLE	156
REVERSE POLARITY TNC MALE	159
REVERSE POLARITY TNC MALE RIGHT ANGLE	159
SHV PLUG	156
SMA FEMALE	157
SMA FEMALE BULKHEAD	157
SMA MALE	156
SMA MALE RIGHT ANGLE	157
SSMC JACK BULKHEAD	157
SSMC PLUG	157
SSMC PLUG RIGHT ANGLE	157
TNC FEMALE	159
TNC FEMALE BULKHEAD	159
TNC MALE	157
TNC MALE RIGHT ANGLE	158
UMCX PLUG RIGHT ANGLE	159
N Male Right Angle To:	
BNC MALE	159
BNC MALE RIGHT ANGLE	159
N FEMALE	160
N FEMALE BULKHEAD	161
N MALE	159
N MALE RIGHT ANGLE	159
NEX10 MALE	162
SMA FEMALE BULKHEAD	162
SMA MALE	161
SMA MALE RIGHT ANGLE	161
TNC FEMALE BULKHEAD	162
TNC MALE	162
TNC MALE RIGHT ANGLE	162
NEX10 Male To:	
NEX10 FEMALE	165
NEX10 FEMALE BULKHEAD	165
NEX10 MALE RIGHT ANGLE	165
NEX10 Male Right Angle To:	
NEX10 FEMALE	165
NEX10 FEMALE BULKHEAD	165
NEX10 MALE RIGHT ANGLE	165
NMO Mount Sexless To:	
TNC MALE	165
QMA Male To:	
QMA FEMALE	166
QMA FEMALE BULKHEAD	166
QMA MALE	165
QMA MALE RIGHT ANGLE	166
SMA FEMALE	166
SMA MALE	166
QMA Male Right Angle To:	
QMA FEMALE	166
QMA FEMALE BULKHEAD	166
QMA MALE RIGHT ANGLE	166
SMA MALE	166
SMA MALE RIGHT ANGLE	166
QN Male To:	
QN MALE	167
QN MALE RIGHT ANGLE	167
QN Male Right Angle To:	
N FEMALE	167
Reverse Polarity SMA Female Bulkhead To:	
HMCX32 1.2 PLUG	200
SMA MALE	200
SMA MALE RIGHT ANGLE	200
UMCX 2.1 PLUG	200
UMCX 2.5 PLUG	200
UMCX PLUG RIGHT ANGLE	200
WMCX 1.6 PLUG	200
Reverse Polarity SMA Male To:	
BNC MALE	186
MCX PLUG RIGHT ANGLE	186
N FEMALE BULKHEAD	187
N MALE	186
REVERSE POLARITY SMA FEMALE	187
REVERSE POLARITY SMA MALE	187
TNC MALE	187
Reverse Polarity SMA Male Right Angle To:	
N MALE	193
N MALE RIGHT ANGLE	193
SMA MALE	193
Reverse Polarity TNC Female To:	
REVERSE POLARITY SMA MALE	215
Reverse Polarity TNC Female Bulkhead To:	
MMCX PLUG	216
REVERSE POLARITY TNC MALE	216
SSMC PLUG RIGHT ANGLE	216
UMCX PLUG	216
Reverse Polarity TNC Male To:	
BNC MALE	214
Reverse Thread SMA Female Bulkhead To:	
UMCX PLUG RIGHT ANGLE	200
Reverse Thread SMA Male To:	
Reverse Thread SMA MALE	187
SC Male To:	
SC MALE	167
SHV Jack Bulkhead To:	
SHV PLUG	168
SHV Plug To:	
SHV JACK BULKHEAD	168
SHV PLUG	167
SMA Female To:	
FAKRA JACK	194
FAKRA PLUG	193
MCX PLUG RIGHT ANGLE	194
MMCX PLUG	194
N FEMALE BULKHEAD	195
N MALE	195
NMO Mount Sexless	195
QMA MALE	195
SMA FEMALE	195
SMA MALE RIGHT ANGLE	195
SMP FEMALE RIGHT ANGLE	196
SSMC JACK BULKHEAD	196
SSMC PLUG	196
SSMC PLUG RIGHT ANGLE	196
Straight Cut Lead Sexless	196
TNC MALE	196
Trimmed Lead Sexless	196
SMA Female 2 Hole Flange To:	
SMA FEMALE 2 HOLE FLANGE	200
SMP FEMALE	200
SMP FEMALE RIGHT ANGLE	200
Straight Cut Lead Sexless	201
Trimmed Lead Sexless	201
SMA Female 4 Hole Flange To:	
BNC FEMALE 4 HOLE FLANGE	201
MMCX PLUG RIGHT ANGLE	201
SMA FEMALE 4 HOLE FLANGE	201
Straight Cut Lead Sexless	201
Trimmed Lead Sexless	201
SMA Female Bulkhead To:	
HMCX32 1.2 PLUG	199
MCX PLUG RIGHT ANGLE	197
MMCX PLUG	197
MMCX PLUG RIGHT ANGLE	197
REVERSE POLARITY SMA MALE	198
SMA FEMALE	197
SMA FEMALE BULKHEAD	198
SMA MALE	197
SMA MALE RIGHT ANGLE	197
SMB PLUG RIGHT ANGLE	198
SMP FEMALE	198
SMP FEMALE RIGHT ANGLE	198
SSMC JACK BULKHEAD	199
SSMC PLUG	198
SSMC PLUG RIGHT ANGLE	199
TNC FEMALE BULKHEAD	199
TNC MALE	199
TNC MALE RIGHT ANGLE	199
UMCX 2.1 PLUG	199

Cable Assembly Locator

Connector Type	Page
SMA Female Bulkhead To:	
UMCX 2.5 PLUG	199
UMCX PLUG RIGHT ANGLE	199
WMCX 1.6 PLUG	199
SMA Male To:	
1.85mm MALE	168
2.4mm MALE	168
2.92mm MALE	168
7/16 DIN MALE	168
BNC MALE	169
BNC MALE RIGHT ANGLE	169
FAKRA JACK	170
FAKRA PLUG	169
HMCX32 1.2 PLUG	185
MC-Card PLUG	171
MINI UHF MALE	171
MMCX PLUG	171
MMCX PLUG RIGHT ANGLE	171
N FEMALE	173
N FEMALE BULKHEAD	173
N MALE	171
N MALE RIGHT ANGLE	172
NMO Mount Sexless	174
QMA MALE	174
REVERSE POLARITY SMA MALE	181
REVERSE POLARITY TNC MALE	185
Reverse Thread SMA MALE	181
SMA FEMALE	178
SMA FEMALE BULKHEAD	179
SMA MALE	174
SMA MALE RIGHT ANGLE	177
SMB JACK	182
SMB PLUG	181
SMB PLUG RIGHT ANGLE	182
SMC PLUG	182
SMP FEMALE	182
SMP FEMALE RIGHT ANGLE	182
SSMA MALE	182
SSMC JACK	183
SSMC JACK BULKHEAD	183
SSMC PLUG	183
SSMC PLUG RIGHT ANGLE	183
Straight Cut Lead Sexless	185
TNC FEMALE	185
TNC FEMALE BULKHEAD	185
TNC MALE	183
TNC MALE RIGHT ANGLE	184
Trimmed Lead Sexless	185
UMCX 2.1 PLUG	186
UMCX 2.5 PLUG	186
UMCX PLUG	185
WMCX 1.6 PLUG	186
SMA Male Right Angle To:	
BNC FEMALE BULKHEAD	188
BNC MALE	187
MCX JACK	188
MCX PLUG RIGHT ANGLE	188
MMCX PLUG RIGHT ANGLE	188
N FEMALE	188
N FEMALE BULKHEAD	188
N MALE	188
N MALE RIGHT ANGLE	188
NEX10 MALE	193
QMA MALE	189
QN FEMALE BULKHEAD	189
REVERSE POLARITY SMA FEMALE	192
REVERSE POLARITY SMA MALE RIGHT ANGLE	192
REVERSE POLARITY TNC MALE RIGHT ANGLE	193
SMA FEMALE	190
SMA FEMALE BULKHEAD	191
SMA MALE	189
SMA MALE RIGHT ANGLE	189
SMB PLUG	192
SMB PLUG RIGHT ANGLE	192
SMC PLUG RIGHT ANGLE	192
SSMC JACK BULKHEAD	192
SSMC PLUG	192
SSMC PLUG RIGHT ANGLE	192
TNC FEMALE BULKHEAD	193
TNC MALE	192
TNC MALE RIGHT ANGLE	192
SMB Plug To:	
BNC MALE	201
N FEMALE	202
SMB JACK BULKHEAD	202
SMB PLUG	202
SMB PLUG RIGHT ANGLE	202
SMB Plug Right Angle To:	
BNC MALE	203
SMA MALE	203
SMB JACK BULKHEAD	203
SMB PLUG RIGHT ANGLE	203
SSMB PLUG	204
SMC Jack Bulkhead To:	
UMCX PLUG RIGHT ANGLE	206
SMC Plug To:	
10-32 MALE RIGHT ANGLE	204
BNC MALE	204
MCX PLUG	204
SMA MALE	204
SMC JACK BULKHEAD	205
SMC PLUG	204
SMC PLUG RIGHT ANGLE	205
SMC Plug Right Angle To:	
BNC MALE	205
SMC JACK BULKHEAD	206
SMC PLUG	205
SMC PLUG RIGHT ANGLE	206
TNC FEMALE BULKHEAD	206
SMP Female To:	
SMA MALE	207
SMP FEMALE	207
SMP FEMALE RIGHT ANGLE	207
SMP Female Right Angle To:	
BNC MALE	207
MMCX PLUG RIGHT ANGLE	207
N FEMALE BULKHEAD	207
REVERSE POLARITY TNC FEMALE BULKHEAD	208
SMA FEMALE	207
SMA FEMALE 2 HOLE FLANGE	207
SMA MALE RIGHT ANGLE	207
SMP FEMALE	208
SMP FEMALE RIGHT ANGLE	208
SMP Male Bulkhead To:	
SMA MALE	206
SMP FEMALE	207
SSMA Male To:	
SSMA MALE	208
SSMA MALE RIGHT ANGLE	208
SSMA Male Right Angle To:	
SSMA MALE RIGHT ANGLE	208
SSMB Plug To:	
SMA MALE	208
SSMB PLUG	208
SSMB Plug Right Angle To:	
SSMB PLUG RIGHT ANGLE	208
SSMC Jack Bulkhead To:	
SSMC JACK BULKHEAD	210
SSMC JACK RIGHT ANGLE BULKHEAD	210
TNC MALE	210
SSMC Jack Right Angle Bulkhead To:	
SSMC JACK RIGHT ANGLE BULKHEAD	210
SSMC Plug To:	
SMB JACK BULKHEAD	209
SSMC JACK BULKHEAD	209
SSMC JACK RIGHT ANGLE BULKHEAD	209
SSMC PLUG	209
SSMC PLUG RIGHT ANGLE	209
TNC MALE	209
SSMC Plug Right Angle To:	
SMA MALE	209
SSMC JACK BULKHEAD	210
SSMC JACK RIGHT ANGLE BULKHEAD	210
SSMC PLUG RIGHT ANGLE	209
TNC FEMALE BULKHEAD	210
TNC MALE	210
TNC Female To:	
NMO Mount Sexless	215
SMA MALE	215
TNC MALE	215
TNC Female Bulkhead To:	
MCX PLUG RIGHT ANGLE	215
MMCX PLUG RIGHT ANGLE	215
SMA MALE	215
SMA MALE RIGHT ANGLE	215
SMC PLUG RIGHT ANGLE	215
SMP FEMALE RIGHT ANGLE	215
SSMC PLUG RIGHT ANGLE	216
TNC FEMALE BULKHEAD	216
TNC MALE	216
UMCX PLUG RIGHT ANGLE	216
TNC Male To:	
BNC MALE	210
MINI UHF MALE	211
N MALE	211
REVERSE POLARITY TNC MALE	213
SMA MALE	211
SMA MALE RIGHT ANGLE	211
TNC FEMALE	213
TNC FEMALE BULKHEAD	213
TNC MALE	211
TNC MALE RIGHT ANGLE	213
TNC Male Right Angle To:	
N FEMALE BULKHEAD	214
N MALE	214
TNC FEMALE	214
TNC FEMALE BULKHEAD	214
TNC MALE	214
TNC MALE RIGHT ANGLE	214
UHF Male To:	
BNC MALE	216
UHF MALE	217
UMCX 2.1 Plug To:	
UMCX 2.1 PLUG	218
UMCX 2.5 Plug To:	
UMCX 2.5 PLUG	218
UMCX Plug Right Angle To:	
MCX JACK BULKHEAD	217
MCX PLUG	217
MCX PLUG RIGHT ANGLE	217
MMCX PLUG RIGHT ANGLE	217
REVERSE POLARITY MCX JACK BULKHEAD	217
SSMB PLUG	217
Straight Cut Lead Sexless	218
WMCX 1.6 Plug To:	
WMCX 1.6 PLUG	218

HIGH-RELIABILITY RF CABLE ASSEMBLIES

Product Features

- Max. Frequency as High as 18 GHz
- Double and Triple Shielded Versions
- Lot Traceability
- J-STD-Soldering
- High-Reliability Cable and Connectors
- RF Test Plots
- Detailed Test Report
- In-Stock and Shipped Same Day

Applications

- Hi-Rel
- MIL-DTL-17 Requirements
- Avionics
- IFF
- SATCOM
- ECM



MIL-DTL-17 Cable Assembly Series



Temperature Conditioned, Low Loss Cable Assembly Series

Pasternack's MIL-DTL-17 Cable Assemblies and Temperature-Conditioned, Low-Loss Cable Assemblies are part of a full line of high-reliability RF components that are in-stock and available for shipment same day. These Commercial-Off-The-Shelf (COTS) assemblies offer a combination of superior materials, processes, and acceptance testing designed to ensure rugged, highly reliable performance for your mission critical applications.

Each assembly is manufactured using J-STD soldering processes and WHMA-A-620 workmanship and is also traceable to its component lots for every material used (RF connectors, coax cable, heat shrink, and solder). There is 100% test sampling of assemblies for connector gaging, insertion loss, VSWR, DWV, workmanship, configuration, and marking, with sampled (AQL) inspections performed for length and mass. A detailed test report accompanies each assembled lot.

Whether the need is to provide a high-reliablity MIL-SPEC connection or a rugged, dependable cable assembly, Pasternack has the right assembly for the job. Visit us online at www.pasternack.com to configure and customize your order, or sign up for our mailing list to receive the latest news and product information.

MIL-DTL-17 BNC CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
M17/28-RG058						
PE3M0115	M17/28-RG058	65.9	BNC, Male	BNC, Male	1	1
PE3M0116				SMA, Male		2
PE3M0117				SMA, Male, RA		3
PE3M0118				TNC, Male		4
M17/60-RG142						
PE3M0001	M17/60-RG142	69.5	BNC, Male	BNC, Male	4	5
PE3M0002				N, Male		6
PE3M0003				N, Female		7
PE3M0004						8
PE3M0005				SMA, Male		9
PE3M0006				SMA, Male, RA		10
PE3M0007				TNC, Male		11
M17/84-RG223						
PE3M0029	M17/84-RG223	65.9	BNC, Male	BNC, Male	4	12
PE3M0030				N, Male		13
PE3M0031				N, Female		14
PE3M0032						15
PE3M0033				SMA, Male		16
PE3M0034				SMA, Male, RA		17
PE3M0035				TNC, Male		18
M17/113-RG316						
PE3M0085	M17/113-RG316	69.5	BNC, Male	BNC, Male	3	19
PE3M0086				SMA, Male		20
PE3M0087				SMA, Male, RA		21
PE3M0088				SMA, Female		22
PE3M0089				TNC, Male		23
M17/119-RG174						
PE3M0100	M17/119-RG174	65.9	BNC, Male	BNC, Male	1	24
PE3M0101				SMA, Male		25
PE3M0102				SMA, Male, RA		26
PE3M0103				SMA, Female		27
PE3M0104				TNC, Male		28
M17/128-RG400						
PE3M0057	M17/128-RG400	69.5	BNC, Male	BNC, Male	4	29
PE3M0058				N, Male		30
PE3M0059				N, Female		31
PE3M0060						32
PE3M0061				SMA, Male		33
PE3M0062				SMA, Male, RA		34
PE3M0063				TNC, Male		35

MIL-DTL-17 N TYPE CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
M17/60-RG142						
PE3M0008	M17/60-RG142	69.5	N, Male	N, Male	11	36
PE3M0009				N, Female		37
PE3M0010						38
PE3M0014				SMA, Male		39
PE3M0015				SMA, Male, RA		40
PE3M0016				TNC, Male		41
PE3M0011			N, Female	N, Female		42
PE3M0012						43
PE3M0013						44
PE3M0017				SMA, Male		45
PE3M0020						46
PE3M0018				SMA, Male, RA		47
PE3M0021						48
PE3M0019				TNC, Male		49
PE3M0022						50
M17/84-RG223						
PE3M0036	M17/84-RG223	65.9	N, Male	N, Male	11	51
PE3M0037				N, Female		52
PE3M0038						53
PE3M0042				SMA, Male		54
PE3M0043				SMA, Male, RA		55
PE3M0044				TNC, Male		56
PE3M0039			N, Female	N, Female		57
PE3M0040						58
PE3M0041						59
PE3M0045				SMA, Male		60
PE3M0048						61
PE3M0046				SMA, Male, RA		62
PE3M0049						63
PE3M0047				TNC, Male		64
PE3M0050						65
M17/128-RG400						
PE3M0064	M17/128-RG400	69.5	N, Male	N, Male	11	66
PE3M0065				N, Female		67
PE3M0066						68
PE3M0070				SMA, Male		69
PE3M0071				SMA, Male, RA		70
PE3M0072				TNC, Male		71
PE3M0067			N, Female	N, Female		72
PE3M0068						73

See Our Website For Current Pricing & Real-Time Stock Availability!

MIL-DTL-17 N TYPE CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
M17/128-RG400						
PE3M0069	M17/128-RG400	69.5	N, Female	N, Female	11	74
PE3M0073				SMA, Male		75
PE3M0076						76
PE3M0074				SMA, Male, RA		77
PE3M0077						78
PE3M0075				TNC, Male		79
PE3M0078						80

MIL-DTL-17 SMA CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
M17/28-RG058						
PE3M0119	M17/28-RG058	65.9	SMA, Male	SMA, Male	1	81
PE3M0120				SMA, Male, RA		82
PE3M0122				TNC, Male		83
PE3M0121			SMA, Male, RA	SMA, Male, RA		84
PE3M0123				TNC, Male		85
M17/60-RG142						
PE3M0023	M17/60-RG142	69.5	SMA, Male	SMA, Male	12.4	86
PE3M0024				SMA, Male, RA		87
PE3M0026				TNC, Male	11	88
PE3M0025			SMA, Male, RA	SMA, Male, RA	12.4	89
PE3M0027				TNC, Male	11	90
M17/84-RG223						
PE3M0051	M17/84-RG223	65.9	SMA, Male	SMA, Male	12.4	91
PE3M0052				SMA, Male, RA		92
PE3M0054				TNC, Male	11	93
PE3M0053			SMA, Male, RA	SMA, Male, RA	12.4	94
PE3M0055				TNC, Male	11	95
M17/113-RG316						
PE3M0090	M17/113-RG316	69.5	SMA, Male	SMA, Male	3	96
PE3M0091				SMA, Male, RA		97
PE3M0092				SMA, Female		98
PE3M0096				TNC, Male		99
PE3M0093			SMA, Male, RA	SMA, Male, RA		1
PE3M0094				SMA, Female		2
PE3M0097				TNC, Male		3
PE3M0095			SMA, Female	SMA, Female		4
PE3M0098				TNC, Male		5
M17/119-RG174						
PE3M0105	M17/119-RG174	65.9	SMA, Male	SMA, Male	1	6
PE3M0106				SMA, Male, RA		7
PE3M0107				SMA, Female		8
PE3M0111				TNC, Male		9
PE3M0108			SMA, Male, RA	SMA, Male, RA		10
PE3M0109				SMA, Female		11
PE3M0112				TNC, Male		12
PE3M0110			SMA, Female	SMA, Female		13
PE3M0113				TNC, Male		14
M17/128-RG400						
PE3M0079	M17/128-RG400	69.5	SMA, Male	SMA, Male	12.4	15
PE3M0080				SMA, Male, RA		16
PE3M0082				TNC, Male	11	17
PE3M0081			SMA, Male, RA	SMA, Male, RA	12.4	18
PE3M0083				TNC, Male	11	19

MIL-DTL-17 TNC CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
M17/28-RG058						
PE3M0124	M17/28-RG058	65.9	TNC, Male	TNC, Male	1	20
M17/60-RG142						
PE3M0028	M17/60-RG142	69.5	TNC, Male	TNC, Male	11	21
M17/84-RG223						
PE3M0056	M17/84-RG223	65.9	TNC, Male	TNC, Male	11	22
M17/113-RG316						
PE3M0099	M17/113-RG316	69.5	TNC, Male	TNC, Male	3	23
M17/119-RG174						
PE3M0114	M17/119-RG174	65.9	TNC, Male	TNC, Male	1	24
M17/128-RG400						
PE3M0084	M17/128-RG400	69.5	TNC, Male	TNC, Male	11	25

TEMPERATURE CONDITIONED, LOW LOSS N TYPE CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
PE-P142LL						
PE3M0174	PE-P142LL	80	N, Male	N, Male	18	26
PE3M0176				N, Male, RA		27
PE3M0175				N, Female		28
PE3M0179			N, Male, RA	N, Male, RA		29
PE3M0178			N, Female			30
PE3M0177				N, Female		31
PE-P160LL						
PE3M0219	PE-P160LL	82.5	N, Male	N, Male	18	32
PE3M0221				N, Male, RA		33
PE3M0220				N, Female		34
PE3M0224			N, Male, RA	N, Male, RA		35
PE3M0223			N, Female			36
PE3M0222				N, Female		37
PE-P300LL						
PE3M0247	PE-P300LL	83	N, Male	N, Male	18	38
PE3M0249				N, Male, RA		39
PE3M0248				N, Female		40
PE3M0252			N, Male, RA	N, Male, RA		41
PE3M0251			N, Female			42
PE3M0250				N, Female		43

TEMPERATURE CONDITIONED, LOW LOSS SMA CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
PE-P142LL						
PE3M0132	PE-P142LL	80	SMA, Male	N, Male	18	44
PE3M0134				N, Male, RA		45
PE3M0133				N, Female		46
PE3M0125				SMA, Male		47
PE3M0128				SMA, Male, RA		48
PE3M0126				SMA, Female		49
PE3M0127						50
PE3M0129				TNC, Male		51
PE3M0131				TNC, Male, RA		52
PE3M0130				TNC, Female		53
PE3M0156			SMA, Male, RA	N, Male		54
PE3M0158				N, Male, RA		55
PE3M0157				N, Female		56
PE3M0152				SMA, Male, RA		57
PE3M0153				TNC, Male		58
PE3M0155				TNC, Male, RA		59
PE3M0154				TNC, Female		60
PE3M0141			SMA, Female	N, Male		61
PE3M0149						62
PE3M0143				N, Male, RA		63
PE3M0151						64
PE3M0142				N, Female		65
PE3M0150						66
PE3M0137				SMA, Male, RA		67
PE3M0145						68
PE3M0135				SMA, Female		69
PE3M0136						70
PE3M0144						71
PE3M0138				TNC, Male		72
PE3M0146						73
PE3M0140				TNC, Male, RA		74
PE3M0148						75
PE3M0139				TNC, Female		76
PE3M0147						77
PE-P160LL						
PE3M0186	PE-P160LL	82.5	SMA, Male	N, Male	18	78
PE3M0188				N, Male, RA		79
PE3M0187				N, Female		80

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz

Notes: Cable assembly max frequency may be lower than connector or coax max frequency

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
PE-P160LL						
PE3M0180	PE-P160LL	82.5	SMA, Male	SMA, Male	18	81
PE3M0182				SMA, Male, RA		82
PE3M0181				SMA, Female		83
PE3M0183				TNC, Male		84
PE3M0185				TNC, Male, RA		85
PE3M0184				TNC, Female		86
PE3M0201			SMA, Male, RA	N, Male		87
PE3M0203				N, Male, RA		88
PE3M0202				N, Female		89
PE3M0197				SMA, Male, RA		90
PE3M0198				TNC, Male		91
PE3M0200				TNC, Male, RA		92
PE3M0199				TNC, Female		93
PE3M0194			SMA, Female	N, Male		94
PE3M0196				N, Male, RA		95
PE3M0195				N, Female		96
PE3M0190				SMA, Male, RA		97
PE3M0189				SMA, Female		98
PE3M0191				TNC, Male		99
PE3M0193				TNC, Male, RA		1
PE3M0192				TNC, Female		2
PE-P300LL						
PE3M0229	PE-P300LL	83	SMA, Male	N, Male	18	3
PE3M0231				N, Male, RA		4
PE3M0230				N, Female		5
PE3M0225				SMA, Male		6
PE3M0226				SMA, Male, RA		7
PE3M0227				TNC, Male		8
PE3M0228				TNC, Male, RA		9
PE3M0235			SMA, Male, RA	N, Male		10
PE3M0237				N, Male, RA		11
PE3M0236				N, Female		12
PE3M0232				SMA, Male, RA		13
PE3M0233				TNC, Male		14
PE3M0234				TNC, Male, RA		15

TEMPERATURE CONDITIONED, LOW LOSS TNC CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
PE-P142LL						
PE3M0162	PE-P142LL	80	TNC, Male	N, Male	18	16

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
PE-P142LL						
PE3M0164	PE-P142LL	80	TNC, Male	N, Male, RA	18	17
PE3M0163				N, Female		18
PE3M0159				TNC, Male		19
PE3M0161				TNC, Male, RA		20
PE3M0160				TNC, Female		21
PE3M0171			TNC, Male, RA	N, Male		22
PE3M0173				N, Male, RA		23
PE3M0172				N, Female		24
PE3M0170				TNC, Male, RA		25
PE3M0167			TNC, Female	N, Male		26
PE3M0169				N, Male, RA		27
PE3M0168				N, Female		28
PE3M0166				TNC, Male, RA		29
PE3M0165				TNC, Female		30
PE-P160LL						
PE3M0207	PE-P160LL	82.5	TNC, Male	N, Male	18	31
PE3M0209				N, Male, RA		32
PE3M0208				N, Female		33
PE3M0204				TNC, Male		34
PE3M0206				TNC, Male, RA		35
PE3M0205				TNC, Female		36
PE3M0216			TNC, Male, RA	N, Male		37
PE3M0218				N, Male, RA		38
PE3M0217				N, Female		39
PE3M0215				TNC, Male, RA		40
PE3M0212			TNC, Female	N, Male		41
PE3M0214				N, Male, RA		42
PE3M0213				N, Female		43
PE3M0211				TNC, Male, RA		44
PE3M0210				TNC, Female		45
PE-P300LL						
PE3M0240	PE-P300LL	83	TNC, Male	N, Male	18	46
PE3M0242				N, Male, RA		47
PE3M0241				N, Female		48
PE3M0238				TNC, Male		49
PE3M0239				TNC, Male, RA		50
PE3M0244			TNC, Male, RA	N, Male		51
PE3M0246				N, Male, RA		52
PE3M0245				N, Female		53
PE3M0243				TNC, Male, RA		54

LOW PIM CABLE ASSEMBLIES

Product Features

- 100% PIM Tested, Results Marked on Cable
- Max Frequency 6 GHz
- Low PIM: < -160 dBc Max
- 76% Phase Velocity
- FEP Jacket
- UL910 Plenum-Rated Cable
- Lightweight and Extremely Flexible
- Low Loss with Excellent VSWR
- IP67 (when mated)
- Shielding Effectivity > 100 dB
- Connector Options: 4.3-10, SMA, QMA, 7/16 DIN, 4.1/9.5, Type-N

Applications

- Low PIM Applications
- Distributed Antenna Systems (DAS)
- Plenum Installations
- Multi-Carrier Communication Systems
- PIM Testing



Low PIM Cable Assemblies

Pasternack's Low PIM Cable Assemblies offer a wide range of connector options: 4.3-10, SMA, QMA, 7/16 DIN, 4.1/9.5, and Type-N. These assemblies deliver low PIM performance to support Distributed Antenna Systems (DAS) and other complex, multi-carrier cable installations. All low PIM assemblies are 100% PIM tested with test results marked on the cable.

Whether the need is to provide a low PIM jumper connection, low PIM test cable, or simply create a custom assembly, Pasternack has the right cable for the job. Low PIM assemblies are part of Pasternack's full line of RF components that are available for same-day shipping. We are continually adding new cables and connectors to the low PIM family. So please visit us online at www.pasternack.com to see the newest additions, or sign up for our mailing list to receive the latest news and product information.

See Our Website For Current Pricing & Real-Time Stock Availability!

SPP Plenum Rated Coax Cable Assemblies

4.1/9.5 SPP PLENUM RATED LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C4143	SPP-250-LLPL	76	4.1/9.5 Mini DIN Male	4.1/9.5 Mini DIN Male	6		1
PE3C5834				4.3-10 Female	5.8	-160	2
PE3C4134				7/16 DIN Male	6		3
PE3C5843			4.1/9.5 Mini DIN Female	N Male	5.8		4
PE3C5844				QMA Male		-150	5
PE3C5845				SMA Male		-155	6

4.3-10 SPP PLENUM RATED LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C4142	SPP-250-LLPL	76	4.3-10 Male	4.3-10 Male	6		7
PE3C6380	SPP-375-LLPL				3		8
PE3C6363	SPP-500-LLPL				5.8		9
PE3C4135	SPP-250-LLPL			7/16 DIN Male	6		10
PE3C6381	SPP-375-LLPL			7/16 DIN Female	3	-160	11
PE3C6365	SPP-500-LLPL			7/16 DIN Male	5.8		12
PE3C5837	SPP-250-LLPL		4.3-10 Female	N Male			13
PE3C6382	SPP-375-LLPL		4.3-10 Male		3		14
PE3C6261	SPP-250-LLPL			NEX10 Male	5.8		15
PE3C5838			4.3-10 Female	QMA Male		-150	16
PE3C5839				SMA Male		-155	17

7/16 DIN SPP PLENUM RATED LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C4130	SPP-250-LLPL	76	7/16 DIN Male	7/16 DIN Male	6		18
PE3C6383	SPP-375-LLPL		7/16 DIN Female	7/16 DIN Female	5.8		19
PE3C6368	SPP-500-LLPL		7/16 DIN Male	7/16 DIN Male			20
PE3C5856	SPP-250-LLPL		7/16 DIN Female	N Male		-160	21
PE3C6384	SPP-375-LLPL						22
PE3C6369	SPP-500-LLPL		7/16 DIN Male				23
PE3C6251	SPP-250-LLPL			NEX10 Male			24
PE3C5857			7/16 DIN Female	QMA Male		-150	25
PE3C5858				SMA Male		-155	26

TYPE-N SPP PLENUM RATED LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C4140	SPP-250-LLPL	76	N Male	4.1/9.5 Mini DIN Male	6	-160	27
PE3C4141				4.3-10 Male			28
PE3C4132				7/16 DIN Male			29
PE3C4137				N Male	5.8	-150	30
PE3C6385	SPP-375-LLPL						31
PE3C6370	SPP-500-LLPL					-160	32
PE3C6254	SPP-250-LLPL		N Female	NEX10 Male			33
PE3C5862			N Male	QMA Female		-150	34
PE3C5881				SMA Female		-160	35

NEX10 SPP PLENUM RATED LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C6253	SPP-250-LLPL	76	NEX10 Male	NEX10 Male	5.8	-160	36

QMA SPP PLENUM RATED LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C5863	SPP-250-LLPL	76	QMA Male	QMA Female	5.8	-150	37
PE3C5864			QMA Female	SMA Male		-155	38

SMA SPP PLENUM RATED LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C5883	SPP-250-LLPL	76	SMA Male	SMA Female	5.8	-155	39
PE3C6258				NEX10 Male		-160	40

PE 1/4 inch SuperFlex Coax Cable Assemblies

2.2-5 PE 1/4 INCH SUPERFLEX LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C7856	1/4" Superflexible	82	2.2-5 Male	2.2-5 Male	6	-150	41
PE3C8051				4.3-10 Male Right Angle		-160	42
PE3C8060				N Male Right Angle			43

4.1/9.5 PE 1/4 INCH SUPERFLEX LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C7819	1/4" Superflexible	82	4.1/9.5 Mini DIN Male	4.1/9.5 Mini DIN Male	6	-150	44

4.3-10 PE 1/4 INCH SUPERFLEX LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C7826	1/4" Superflexible	82	4.3-10 Male	4.3-10 Male	6	-150	45

7/16 DIN PE 1/4 INCH SUPERFLEX LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C0377	1/4" Superflexible	82	7/16 DIN Male	N Male	3		46
PE3C7835				7/16 DIN Male	6	-150	47

TYPE-N PE 1/4 INCH SUPERFLEX LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C0124	1/4" Superflexible	82	N Male	N Male	3		48
PE3C2897				Straight Cut Lead			49

NEX10 PE 1/4 INCH SUPERFLEX LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C7849	1/4" Superflexible	82	NEX10 Male	NEX10 Male	6	-150	50

QMA PE 1/4 INCH SUPERFLEX LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C7870	1/4" Superflexible	82	QMA Male	QMA Male	6	-150	51

SMA PE 1/4 INCH SUPERFLEX LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C7863	1/4" Superflexible	82	SMA Male	SMA Male	6	-150	52

SPF Fire Rated Coax Cable Assemblies

4.3-10 SPF FIRE RATED LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C6348	SPF-250	83	4.3-10 Female	4.3-10 Female	5.8	-160	53
PE3C6445	SPF-375		4.3-10 Male	4.3-10 Male	6	-158	54
PE3C6516	SPF-500						55
PE3C6350	SPF-250		4.3-10 Female	7/16 DIN Male	5.8	-160	56
PE3C6506	SPF-375		4.3-10 Male		6	-158	57
PE3C6515	SPF-500						58
PE3C6351	SPF-250		4.3-10 Female	N Male	5.8	-160	59
PE3C6505	SPF-375		4.3-10 Male	N Female	6	-158	60
PE3C6353	SPF-250		4.3-10 Female	NEX10 Male	5.8	-160	61

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

7/16 DIN SPF FIRE RATED LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C6356	SPF-250	83	7/16 DIN Male	7/16 DIN Male	5.8	-160	62
PE3C6508	SPF-375				6	-158	63
PE3C6514	SPF-500						64
PE3C6357	SPF-250			N Male	5.8	-160	65
PE3C8496	SPF-375				6		66
PE3C6359	SPF-250			NEX10 Male	5.8		67

TYPE-N SPF FIRE RATED LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C6360	SPF-250	83	N Male	N Male	5.8	-160	68
PE3C6379	SPF-375		N Female	N Female	6		69
PE3C6374	SPF-500		N Male	N Male			70
PE3C6362	SPF-250			NEX10 Male	5.8		71

NEX10 SPF FIRE RATED LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3W08531	SPF-250	83	NEX10 Male	NEX10 Male	5.8	-160	72

SPO Outdoor Rated Coax Cable Assemblies

4.3-10 SPO OUTDOOR RATED LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C6331	SPO-250	83	4.3-10 Female	4.3-10 Female	5.8	-160	73
PE3C6498	SPO-375		4.3-10 Male	4.3-10 Male	3	-158	74
PE3C6513	SPO-500				6		75
PE3C6333	SPO-250		4.3-10 Female	7/16 DIN Male	5.8	-160	76
PE3C6500	SPO-375		4.3-10 Male		3	-158	77
PE3C6512	SPO-500				6		78
PE3C6336	SPO-250		4.3-10 Female	N Male	5.8	-160	79
PE3C6499	SPO-375		4.3-10 Male	N Female	3	-158	80
PE3C6338	SPO-250		4.3-10 Female	NEX10 Male	5.8	-160	81

7/16 DIN SPO OUTDOOR RATED LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C6341	SPO-250	83	7/16 DIN Male	7/16 DIN Male	5.8	-160	82
PE3C6502	SPO-375				3	-158	83
PE3C6511	SPO-500				6		84
PE3C6342	SPO-250			N Male	5.8	-160	85
PE3C8513	SPO-375			N Female	6		86
PE3C6344	SPO-250			NEX10 Male	5.8		87

TYPE-N SPO OUTDOOR RATED LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C6345	SPO-250	83	N Male	N Male	5.8	-160	88
PE3C6378	SPO-375		N Female	N Female	6		89
PE3C6371	SPO-500		N Male	N Male			90
PE3C6347	SPO-250			NEX10 Male	5.8		91

NEX10 SPO OUTDOOR RATED LOW PIM CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C6347-1	SPO-250	83	NEX10 Male	N Male	5.8	-160	92
PE3C6338-1				4.3-10 Female			93
PE3C6344-1				7/16 DIN Male			94

Flexible Low PIM Plenum Rated Coax Assemblies

1.0/2.3 FLEXIBLE LOW PIM PLENUM RATED CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C7947	TFT-402	76	1.0/2.3 Plug	1.0/2.3 Plug	5.8	-150	95
PE3C7979	TFT-402-LF						96

2.2-5 FLEXIBLE LOW PIM PLENUM RATED CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C7948	TFT-402	76	2.2-5 Male	2.2-5 Male	5.8	-160	97
PE3C7980	TFT-402-LF				3		98
PE3C8381	TFT-402			N Male	5.8		99
PE3C8389	TFT-402-LF						1

4.1/9.5 FLEXIBLE LOW PIM PLENUM RATED CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C7950	TFT-402	76	4.1/9.5 Mini DIN Male	4.1/9.5 Mini DIN Male	3	-160	2
PE3C7982	TFT-402-LF						3
PE3C8214	TFT-402		4.1/9.5 Mini DIN Female	4.3-10 Male	5.8		4
PE3C8275	TFT-402-LF						5
PE3C8229	TFT-402			7/16 DIN Male			6
PE3C8283	TFT-402-LF						7
PE3C8235	TFT-402			N Male			8
PE3C8289	TFT-402-LF						9

4.3-10 FLEXIBLE LOW PIM PLENUM RATED CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C7952	TFT-402	76	4.3-10 Male	4.3-10 Male	5.8	-160	10
PE3C8241			4.3-10 Female	7/16 DIN Male			11
PE3C8253				N Male			12
PE3C7984	TFT-402-LF		4.3-10 Male	4.3-10 Male			13
PE3C8295			4.3-10 Female	7/16 DIN Male			14
PE3C8307				N Male			15

7/16 DIN FLEXIBLE LOW PIM PLENUM RATED CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C7959	TFT-402	76	7/16 DIN Male	7/16 DIN Male	5.8	-160	16
PE3C7991	TFT-402-LF						17
PE3C8265	TFT-402		7/16 DIN Female	N Male			18
PE3C8319	TFT-402-LF						19

TYPE-N FLEXIBLE LOW PIM PLENUM RATED CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C7966	TFT-402	76	N Male	N Male	5.8	-160	20
PE3C7998	TFT-402-LF						21
PE3C8343	TFT-402			QMA Male	3	-150	22

NEX10 FLEXIBLE LOW PIM PLENUM RATED CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C7971	TFT-402	76	NEX10 Male	NEX10 Male	5.8	-160	23
PE3C8003	TFT-402-LF						24

QMA FLEXIBLE LOW PIM PLENUM RATED CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C7973	TFT-402	76	QMA Male	QMA Male	3	-150	25

SMA FLEXIBLE LOW PIM PLENUM RATED CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
PE3C7976	TFT-402	76	SMA Male	SMA Male	5.8	-150	26

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

1.0/2.3 PLUG TO BNC FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W05192				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		1
12"	24"	36"	48"	60"	50CM	Custom Len.	
$48.39	$49.39	$50.99	$51.99	$51.99	$48.99	See Web	

1.0/2.3 PLUG RIGHT ANGLE TO BNC MALE



Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C3469				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	2
12"	24"	36"	48"	60"	50CM	Custom Len.	
$57.99	$57.99	$61.99	$64.99	$68.99	$56.99	See Web	

1.0/2.3 JACK BULKHEAD TO 1.0/2.3 JACK BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C0441				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	3
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.99	$62.99	$66.99	$70.99	$73.99	$77.99	See Web	

1.0MM MALE TO 1.0MM MALE



Precision Flexible Cable Assemblies

PE-110TC Coax, 50 Ohm

Part No. PE3TC1220				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.							4
6"	12"	24"	-	-	-	Custom Len.	
$7,360.00	$9,850.00	Call	-	-	-	See Web	

1.0MM MALE TO 1.0MM FEMALE



Precision Flexible Cable Assemblies

PE-110TC Coax, 50 Ohm

Part No. PE3TC1221				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.							5
6"	12"	18"	-	-	-	Custom Len.	
Call	$7,690.00	Call	-	-	-	See Web	

1.85MM MALE TO 1.85MM MALE



Skew Matched Pair Flexible Cable Assemblies

PE-P106LL Coax, 50 Ohm

Part No. PE3C5835				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.106" dia.			6
12"	36"	48"	-	-	-	Custom Len.	
$3,990.00	$5,110.00	$5,370.00	-	-	-	See Web	

Low Loss Flexible Cable Assemblies

PE-P106LL Coax, 50 Ohm

Part No. PE3C5998				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.106" dia.			7
6"	12"	24"	36"	50CM	100CM	Custom Len.	
$730.00	$755.00	$755.00	$830.00	$730.00	$855.00	See Web	

Low Loss Semi-Rigid Cable Assemblies

PECX001 Coax, 50 Ohm

Part No. PE3C6484				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					30 dB/100ft	101 W	8
6"	12"	18"	24"	36"	48"	Custom Len.	
$339.99	$339.99	$339.99	$341.99	$341.99	$343.99	See Web	

PECX002 Coax, 50 Ohm

Part No. PE3C6487				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					30 dB/100ft	101 W	9
6"	12"	18"	24"	60"	-	Custom Len.	
$345.99	$345.99	$345.99	$345.99	$351.99	-	See Web	

PECX003 Coax, 50 Ohm

Part No. PE3C6490				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					20 dB/100ft	188 W	10
6"	12"	18"	48"	60"	-	Custom Len.	
$347.99	$347.99	$349.99	$353.99	$355.99	-	See Web	

PECX004 Coax, 50 Ohm

Part No. PE3C6491				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					20 dB/100ft	188 W	11
6"	12"	18"	24"	48"	60"	Custom Len.	
$351.99	$351.99	$351.99	$353.99	$357.99	$359.99	See Web	

Precision Flexible Cable Assemblies

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC0800				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.27" dia.			12
30CM	60CM	24"	36"	48"	241"	Custom Len.	
Call	Call	$3,620.00	$3,320.00	$3,790.00	Call	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE36521				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	13
6"	12"	18"	24"	36"	48"	Custom Len.	
$457.99	$457.99	$461.99	$465.99	$475.99	$483.99	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE36525				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	14
6"	12"	18"	24"	36"	48"	Custom Len.	
$405.99	$405.99	$411.99	$419.99	$431.99	$445.99	See Web	

Standard Flexible Cable Assemblies

PE-P086 Coax, 50 Ohm

Part No. PE3C0752				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	23 dB/100ft	160 W	15
12"	24"	36"	48"	60"	50CM	Custom Len.	
$277.99	$287.99	$297.99	$307.99	$289.99	$265.99	See Web	

PE-P103 Coax, 50 Ohm

Part No. PE3C6638				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.103" dia.	29.48 dB/100ft		16
12"	24"	36"	48"	50CM	200CM	Custom Len.	
$315.99	$347.99	$379.99	$411.99	$347.99	$515.00	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE36519				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	17
6"	12"	18"	24"	36"	48"	Custom Len.	
$481.99	$461.99	$467.99	$505.00	$485.99	$497.99	See Web	

RG405/U Coax, 50 Ohm

Part No. PE36523				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	18
6"	12"	18"	24"	36"	48"	Custom Len.	
$409.99	$409.99	$413.99	$417.99	$425.99	$433.99	See Web	

1.85MM MALE TO 1.85MM MALE RIGHT ANGLE



Precision Flexible Cable Assemblies

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC1000				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.27" dia.			19
24"	36"	48"	-	-	-	Custom Len.	
$4,200.00	Call	$4,380.00	-	-	-	See Web	

1.85MM MALE TO 1.85MM FEMALE



Precision Flexible Cable Assemblies

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC0900				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.27" dia.			20
24"	36"	48"	-	-	-	Custom Len.	
$3,620.00	$3,620.00	$3,790.00	-	-	-	See Web	

1.85MM MALE TO 2.4MM MALE



Standard Flexible Cable Assemblies

PE-P103 Coax, 50 Ohm

Part No. PE3C6639				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.103" dia.	29.48 dB/100ft		21
24"	36"	48"	60"	-	-	Custom Len.	
$363.99	$395.99	$427.99	$459.99	-	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

***Coax Performance at 1 GHz** **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

1.85MM MALE TO 2.92MM MALE



Low Loss Semi-Rigid Cable Assemblies

PECX001 Coax, 50 Ohm

Part No. PE3C6485				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					30 dB/100ft	101 W	22
6"	12"	18"	24"	36"	-	Custom Len.	
$329.99	$329.99	$329.99	$331.99	$331.99	-	See Web	

PECX002 Coax, 50 Ohm

Part No. PE3C6488				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					30 dB/100ft	101 W	23
6"	12"	18"	24"	36"	60"	Custom Len.	
$335.99	$335.99	$335.99	$335.99	$337.99	$341.99	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W07895				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	24
24"	36"	60"	100CM	150CM	200CM	Custom Len.	
$307.99	$317.99	$339.99	$321.99	$337.99	$355.99	See Web	

2.2-5 MALE TO 2.2-5 MALE RIGHT ANGLE



Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7857				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		25
12"	24"	36"	48"	60"	50CM	Custom Len.	
$87.99	$91.99	$96.99	$101.99	$105.99	$90.99	See Web	

2.2-5 MALE TO 2.2-5 FEMALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7949				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			26
12"	24"	36"	48"	60"	50CM	Custom Len.	
$85.99	$89.99	$94.99	$98.99	$103.99	$83.99	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7858				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		27
12"	24"	36"	48"	60"	50CM	Custom Len.	
$79.99	$84.99	$88.99	$92.99	$97.99	$82.99	See Web	

2.2-5 MALE TO 2.2-5 FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Flexible Cable Assemblies

TFT-402-LF Coax, 50 Ohm

Part No. PE3C7981				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			28
12"	24"	36"	48"	60"	50CM	Custom Len.	
$80.99	$83.99	$85.99	$88.99	$90.99	$79.99	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7859				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		29
12"	24"	36"	48"	60"	50CM	Custom Len.	
$82.99	$87.99	$91.99	$95.99	$101.99	$85.99	See Web	

2.2-5 MALE TO N MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8382				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			30
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.99	$68.99	$72.99	$76.99	$80.99	$66.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8390				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			31
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.99	$64.99	$66.99	$68.99	$71.99	$63.99	See Web	

2.2-5 MALE TO N FEMALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8383				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			32
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$64.99	$69.99	$73.99	$77.99	$63.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8391				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			33
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$61.99	$63.99	$65.99	$68.99	$60.99	See Web	

2.2-5 MALE TO N FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8384				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			34
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.99	$66.99	$70.99	$74.99	$79.99	$65.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8392				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			35
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$62.99	$64.99	$67.99	$69.99	$61.99	See Web	

2.2-5 MALE RIGHT ANGLE TO 2.2-5 MALE RIGHT ANGLE



Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7860				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		36
12"	24"	36"	48"	60"	50CM	Custom Len.	
$95.99	$99.99	$103.99	$107.99	$113.99	$97.99	See Web	

2.2-5 MALE RIGHT ANGLE TO 2.2-5 FEMALE



Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7861				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		37
12"	24"	36"	48"	60"	50CM	Custom Len.	
$87.99	$91.99	$96.99	$101.99	$105.99	$90.99	See Web	

2.2-5 MALE RIGHT ANGLE TO 2.2-5 FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7862				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		38
12"	24"	36"	48"	60"	50CM	Custom Len.	
$91.99	$95.99	$101.99	$105.99	$109.99	$94.99	See Web	

2.2-5 FEMALE TO 4.3-10 MALE RIGHT ANGLE



Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C8056				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		39
12"	24"	36"	48"	60"	50CM	Custom Len.	
$85.99	$89.99	$94.99	$98.99	$103.99	$84.99	See Web	

2.2-5 FEMALE TO N MALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8385				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			40
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.99	$66.99	$70.99	$74.99	$79.99	$65.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8393				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			41
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$62.99	$64.99	$67.99	$69.99	$61.99	See Web	

2.2-5 FEMALE TO N MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8386				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			42
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.99	$68.99	$72.99	$76.99	$80.99	$66.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8394				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			43
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.99	$64.99	$66.99	$68.99	$71.99	$63.99	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C8064				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		44
12"	24"	36"	48"	60"	50CM	Custom Len.	
$80.99	$84.99	$88.99	$92.99	$97.99	$78.99	See Web	

2.2-5 FEMALE TO N FEMALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8387				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			45
12"	24"	36"	48"	60"	50CM	Custom Len.	
$61.99	$65.99	$69.99	$73.99	$77.99	$63.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8395				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			46
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$61.99	$63.99	$65.99	$68.99	$60.99	See Web	

2.2-5 FEMALE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8388				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			47
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.99	$66.99	$70.99	$74.99	$79.99	$65.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8396				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			48
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$62.99	$64.99	$67.99	$69.99	$61.99	See Web	

2.4MM MALE TO 1.85MM MALE



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W08014					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.105" dia.	19.5 dB/100ft	121.5 W	49
18"	24"	36"	50CM	150CM	-		Custom Len.	
$311.99	$317.99	$327.99	$313.99	$347.99	-		See Web	

2.4MM MALE TO 2.92MM MALE



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W08333					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.105" dia.	19.5 dB/100ft	121.5 W	50
50CM	-	-	-	-	-		Custom Len.	
$227.99	-	-	-	-	-		See Web	

2.4MM MALE TO 2.4MM MALE



Precision Flexible Cable Assemblies

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC0500					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.27" dia.			51
24"	36"	48"	-		-	-	Custom Len.	
$3,500.00	Call	$3,670.00	-		-	-	See Web	

Test Flexible Cable Assemblies

PE-P160 Coax, 50 Ohm

Part No. PE363				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.	12.62 dB/100ft		52
12"	24"	36"	48"	60"	50CM	Custom Len.	
Call	Call	$417.99	$449.99	Call	Call	See Web	

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA4004				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			53
24"	48"	100CM	700CM	-	-	Custom Len.	
$2,470.00	$2,730.00	Call	Call	-	-	See Web	

Standard Flexible Cable Assemblies

PE-P086HF Coax, 50 Ohm

Part No. PE3C7803				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.104" dia.	21.1 dB/100ft		54
12"	24"	36"	48"	60"	50CM	Custom Len.	
$271.99	$279.99	$289.99	$299.99	$307.99	$267.99	See Web	

PE-P103 Coax, 50 Ohm

Part No. PE3C6640				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.103" dia.	29.48 dB/100ft		55
12"	24"	36"	48"	60"	50CM	Custom Len.	
$331.99	$363.99	$377.99	$409.99	$461.99	$345.99	See Web	

2.4MM MALE TO 2.4MM MALE RIGHT ANGLE



Precision Flexible Cable Assemblies

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC0700				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.27" dia.			56
24"	36"	48"	-	-	-	Custom Len.	
$4,090.00	Call	$4,260.00	-	-	-	See Web	

2.4MM MALE TO 2.4MM FEMALE



Precision Flexible Cable Assemblies

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC0600				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.27" dia.			57
24"	36"	48"	-	-	-	Custom Len.	
$3,530.00	Call	$3,710.00	-	-	-	See Web	

Test Flexible Cable Assemblies

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA4005				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			58
24"	48"	-	-	-	-	Custom Len.	
$2,650.00	$2,920.00	-	-	-	-	See Web	

Standard Flexible Cable Assemblies

PE-P160 Coax, 50 Ohm

Part No. PE364				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.155" dia.	12.62 dB/100ft	1,070 W	59
12"	24"	36"	48"	60"	50CM	Custom Len.	
Call	Call	$433.99	$457.99	Call	Call	See Web	

2.4MM MALE TO SMA MALE



Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3W08574					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22 dB/100ft	130 W	60
48"	-	-	-		-	-	Custom Len.	
$203.99	-	-	-		-	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

2.4MM FEMALE BULKHEAD TO SMA MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE3W03550				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	61
12"	24"	36"	48"	60"	50CM	Custom Len.	
$211.99	$225.99	$239.99	$253.99	$267.99	$219.99	See Web	

2.4MM NMD FEMALE TO 2.4MM MALE



Precision Flexible Cable Assemblies

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC0660				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.27" dia.			62
24"	70"	-	-	-	-	Custom Len.	
Call	Call	-	-	-	-	See Web	

2.4MM NMD FEMALE TO 2.4MM FEMALE



Precision Flexible Cable Assemblies

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC0670				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.27" dia.			63
24"	48"	-	-	-	-	Custom Len.	
Call	$4,280.00	-	-	-	-	See Web	

2.92MM MALE TO 1.85MM MALE



Standard Flexible Cable Assemblies

PE-P103 Coax, 50 Ohm

Part No. PE3C6636				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.103" dia.	29.48 dB/100ft		64
48"	50CM	100CM	200CM	-	-	Custom Len.	
$381.99	$307.99	$359.99	$459.99	-	-	See Web	

2.92MM MALE TO 2.4MM MALE



Standard Flexible Cable Assemblies

PE-P103 Coax, 50 Ohm

Part No. PE3C6637				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.103" dia.	29.48 dB/100ft		65
24"	36"	48"	60"	50CM	100CM	Custom Len.	
$293.99	$323.99	$355.99	$401.99	$293.99	$333.99	See Web	

2.92MM MALE TO 2.92MM MALE



Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C0835					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22 dB/100ft	130 W	66
6"	12"	18"	24"	36"	48"	Custom Len.		
Call	Call	Call	Call	Call	Call	See Web		

Skew Matched Pair Flexible Cable Assemblies

PE-P141LL Coax, 50 Ohm

Part No. PE3CA2517				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.			67
12"	24"	36"	48"	600CM	-	Custom Len.	
$640.00	$730.00	$815.00	$905.00	Call	-	See Web	

Low Loss Semi-Rigid Cable Assemblies

PECX001 Coax, 50 Ohm

Part No. PE3C6486					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						30 dB/100ft	101 W	68
6"	12"	18"	24"	36"	48"	Custom Len.		
$319.99	$319.99	$319.99	$321.99	$321.99	$323.99	See Web		

PECX002 Coax, 50 Ohm

Part No. PE3C6489					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						30 dB/100ft	101 W	69
6"	12"	18"	24"	48"	60"	Custom Len.		
$325.99	$325.99	$325.99	$325.99	$329.99	$331.99	See Web		

PECX005 Coax, 50 Ohm

Part No. PE3C6492					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						17 dB/100ft	314 W	70
6"	12"	18"	24"	36"	48"	Custom Len.		
$315.99	$315.99	$315.99	$317.99	$317.99	$319.99	See Web		

PECX006 Coax, 50 Ohm

Part No. PE3C6493					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						17 dB/100ft	231 W	71
6"	12"	18"	24"	36"	60"	Custom Len.		
$319.99	$319.99	$319.99	$319.99	$321.99	$323.99	See Web		

Test Flexible Cable Assemblies

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA2605				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			72
24"	48"	-	-	-	-	Custom Len.	
Call	$2,110.00	-	-	-	-	See Web	

Part No. PE3VNA4001				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			73
-	24"	36"	48"	60"	50CM	Custom Len.	
-	$2,190.00	$2,500.00	$2,690.00	$2,830.00	Call	See Web	

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE34733				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	74
6"	12"	18"	24"	36"	48"	Custom Len.	
$159.99	$163.99	$167.99	$163.99	$183.99	$181.99	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3C1377				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	75
6"	12"	18"	24"	36"	48"	Custom Len.	
$203.99	$203.99	$209.99	$215.99	$229.99	$241.99	See Web	

Standard Flexible Cable Assemblies

PE-P086 Coax, 50 Ohm

Part No. PE3C0666				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.104" dia.	23 dB/100ft	160 W	76
6"	12"	18"	24"	36"	48"	Custom Len.	
$199.99	$203.99	$209.99	$213.99	$223.99	$233.99	See Web	

PE-P103 Coax, 50 Ohm

Part No. PE3C6635				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.103" dia.	29.48 dB/100ft		77
12"	24"	36"	48"	300CM	-	Custom Len.	
$309.99	$341.99	$361.99	$407.99	$580.00	-	See Web	

PE-P160 Coax, 50 Ohm

Part No. PE360				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.155" dia.	12.62 dB/100ft	1,070 W	78
12"	24"	36"	48"	60"	72"	Custom Len.	
$281.99	$309.99	$335.99	$361.99	$387.99	$411.99	See Web	

Standard Semi-Rigid Cable Assemblies

PE-118SR Coax, 50 Ohm

Part No. PE3W07491				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12.5 dB/100ft	500 W	79
6"	12"	18"	24"	36"	60"	Custom Len.	
$345.99	$345.99	$347.99	$349.99	$355.99	$363.99	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34731				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	80
6"	12"	18"	24"	36"	48"	Custom Len.	
$159.99	$155.99	$161.99	$177.99	$179.99	$191.99	See Web	

RG402/U Coax, 50 Ohm

Part No. PE34729				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	81
6"	12"	18"	24"	36"	48"	Custom Len.	
$161.99	$165.99	$171.99	$175.99	$185.99	$183.99	See Web	

2.92MM MALE TO 2.92MM FEMALE



Test Flexible Cable Assemblies

PE-P160 Coax, 50 Ohm

Part No. PE361				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.	12.62 dB/100ft		82
12"	24"	36"	48"	60"	50CM	Custom Len.	
$329.99	$361.99	$393.99	$425.99	$457.99	$349.99	See Web	

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA2606				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			83
48"	-	-	-	-	-	Custom Len.	
Call	-	-	-	-	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

Part No. PE3VNA4002				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			84
24"	48"	-	-	-	-	Custom Len.	
$2,250.00	$2,750.00	-	-	-	-	See Web	

2.92MM MALE TO 2.92MM FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE34745				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	85
6"	12"	18"	24"	36"	48"	Custom Len.	
$245.99	$245.99	$249.99	$253.99	$263.99	$271.99	See Web	

Standard Semi-Rigid Cable Assemblies

PE-SR402AL Coax, 50 Ohm

Part No. PE34743				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	86
6"	12"	18"	24"	36"	48"	Custom Len.	
$265.99	$247.99	$277.99	$283.99	$269.99	$281.99	See Web	

2.92MM NMD FEMALE TO 2.92MM MALE



Test Flexible Cable Assemblies

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA4007				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			87
24"	36"	48"	-	-	-	Custom Len.	
$2,880.00	$2,980.00	$3,110.00	-	-	-	See Web	

2.92MM NMD FEMALE TO 2.92MM FEMALE



Test Flexible Cable Assemblies

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA4008				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			88
24"	36"	48"	-	-	-	Custom Len.	
$2,920.00	$3,060.00	$3,180.00	-	-	-	See Web	

3.5MM MALE TO 1.85MM MALE



Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE36537				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	89
6"	12"	18"	24"	36"	48"	Custom Len.	
$317.99	$325.99	$331.99	$337.99	$349.99	$361.99	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE36535				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	90
6"	12"	18"	24"	36"	48"	Custom Len.	
$321.99	$325.99	$329.99	$333.99	$343.99	$351.99	See Web	

3.5MM MALE TO 3.5MM MALE



Test Flexible Cable Assemblies

PE-P160 Coax, 50 Ohm

Part No. PE369				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.	12.62 dB/100ft		91
12"	24"	36"	48"	60"	50CM	Custom Len.	
Call	Call	$379.99	$411.99	$443.99	Call	See Web	

PE-VNA Coax, 50 Ohm

Part No. PE315					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.								92
24"	36"	48"	60"	72"	100CM	Custom Len.		
$1,270.00	$1,520.00	$1,510.00	$1,760.00	$1,920.00	Call	See Web		

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA2603				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			93
24"	36"	48"	60"	-	-	Custom Len.	
$1,830.00	$2,150.00	$2,080.00	$2,410.00	-	-	See Web	

Standard Semi-Rigid Cable Assemblies

PE-SR402AL Coax, 50 Ohm

Part No. PE34572				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	94
6"	12"	18"	24"	36"	48"	Custom Len.	
$269.99	$275.99	$281.99	$289.99	$301.99	$295.99	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34576				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	95
6"	12"	18"	24"	36"	48"	Custom Len.	
$271.99	$271.99	$277.99	$281.99	$293.99	$303.99	See Web	

RG402/U Coax, 50 Ohm

Part No. PE34570				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	96
6"	12"	18"	24"	36"	48"	Custom Len.	
$263.99	$263.99	$267.99	$271.99	$281.99	$289.99	See Web	

RG405/U Coax, 50 Ohm

Part No. PE34574				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	97
6"	12"	18"	24"	36"	48"	Custom Len.	
$275.99	$275.99	$279.99	$283.99	$291.99	$319.99	See Web	

3.5MM MALE TO 3.5MM FEMALE



Test Flexible Cable Assemblies

PE-VNA Coax, 50 Ohm

Part No. PE317					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.								98
24"	36"	48"	60"	72"	-	Custom Len.		
$1,280.00	$1,370.00	$1,650.00	$1,600.00	$1,790.00	-	See Web		

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA2604				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			99
24"	36"	48"	60"	-	-	Custom Len.	
$1,870.00	$2,190.00	$2,110.00	$2,450.00	-	-	See Web	

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE35121				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	1
12"	24"	36"	48"	60"	-	Custom Len.	
$279.99	$273.99	$283.99	$291.99	$301.99	-	See Web	

Part No. PE3W03922				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	400 W	2
12"	24"	36"	48"	60"	50CM	Custom Len.	
$231.99	$239.99	$249.99	$259.99	$269.99	$237.99	See Web	

Standard Flexible Cable Assemblies

PE-FF430 Coax, 50 Ohm

Part No. PE3C4012					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.43" dia.			3
100CM	-	-	-	-	-	Custom Len.		
$1,100.00	-	-	-	-	-	See Web		

Standard Semi-Rigid Cable Assemblies

PE-SR402AL Coax, 50 Ohm

Part No. PE34580				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	4
6"	12"	18"	24"	36"	48"	Custom Len.	
$267.99	$267.99	$273.99	$277.99	$289.99	$319.99	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34584				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	5
6"	12"	18"	24"	36"	48"	Custom Len.	
Call	$333.99	Call	$343.99	$353.99	$363.99	See Web	

RG402/U Coax, 50 Ohm

Part No. PE34578				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	6
6"	12"	18"	24"	36"	48"	Custom Len.	
$281.99	$269.99	$273.99	$277.99	$287.99	$295.99	See Web	

RG405/U Coax, 50 Ohm

Part No. PE34582				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	7
6"	12"	18"	24"	36"	48"	Custom Len.	
$357.99	$357.99	$361.99	$365.99	$375.99	$407.99	See Web	

3.5MM MALE TO 3.5MM FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Semi-Rigid Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

***Coax Performance at 1 GHz** **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

For our complete selection of cable assemblies, please visit our website

PE-SR402AL Coax, 50 Ohm — 8

Part No. PE34588				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W
6"	12"	18"	24"	36"	48"	Custom Len.
$469.99	$475.99	$481.99	$487.99	$497.99	$510.00	See Web

PE-SR405AL Coax, 50 Ohm — 9

Part No. PE34592				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W
6"	12"	18"	24"	36"	48"	Custom Len.
$281.99	$287.99	$291.99	$297.99	$307.99	$317.99	See Web

RG402/U Coax, 50 Ohm — 10

Part No. PE34586				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W
6"	12"	18"	24"	36"	48"	Custom Len.
$477.99	$483.99	$487.99	$491.99	$499.99	$510.00	See Web

RG405/U Coax, 50 Ohm — 11

Part No. PE34590				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W
6"	12"	18"	24"	36"	48"	Custom Len.
$287.99	$291.99	$295.99	$299.99	$307.99	$315.99	See Web

3.5MM FEMALE TO 2.92MM MALE



Standard Semi-Rigid Cable Assemblies

PE-SR402AL Coax, 50 Ohm — 12

Part No. PE3W08060						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.							13 dB/100ft	450 W
24"	36"	150CM	-	-	-	Custom Len.		
$215.99	$227.99	$249.99	-	-	-	See Web		

3.5MM FEMALE TO 3.5MM FEMALE



Standard Flexible Cable Assemblies

PE-FF430 Coax, 50 Ohm — 13

Part No. PE3C4013						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						0.43" dia.		
100CM	-	-	-	-	-	Custom Len.		
$1,080.00	-	-	-	-	-	See Web		

3.5MM FEMALE TO 3.5MM NMD FEMALE



Test Flexible Cable Assemblies

PE-VNA-R Coax, 50 Ohm — 14

Part No. PE3VNA2610						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						0.43" dia.		
24"	36"	48"	-	-	-	Custom Len.		
$2,170.00	$2,300.00	$2,420.00	-	-	-	See Web		

3.5MM NMD FEMALE TO 3.5MM MALE



Test Flexible Cable Assemblies

PE-VNA-R Coax, 50 Ohm — 15

Part No. PE3VNA2607						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						0.43" dia.		
24"	36"	48"	-	-	-	Custom Len.		
$2,130.00	$2,260.00	$2,380.00	-	-	-	See Web		

4.1/9.5 MINI DIN MALE TO 4.1/9.5 MINI DIN MALE



Low PIM Formable Cable Assemblies

PE-SR402FLJ Low PIM Coax, 50 Ohm — 16

Part No. PE3C2009						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						0.161" dia.		
50CM	100CM	200CM	-	-	-	Custom Len.		
Call	$129.99	$155.99	-	-	-	See Web		

4.1/9.5 MINI DIN MALE TO 4.1/9.5 MINI DIN MALE RIGHT ANGLE



Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm — 17

Part No. PE3C7820				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$81.99	$85.99	$89.99	$94.99	$98.99	$83.99	See Web

SPP-250-LLPL Coax, 50 Ohm — 18

Part No. PE3C5847				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$121.99	$127.99	$133.99	$139.99	$147.99	$123.99	See Web

4.1/9.5 MINI DIN MALE TO 4.1/9.5 MINI DIN FEMALE



Low PIM Formable Cable Assemblies

PE-SR402FLJ Low PIM Coax, 50 Ohm — 19

Part No. PE3C2010						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						0.161" dia.		
100CM	200CM	-	-	-	-	Custom Len.		
$159.99	Call	-	-	-	-	See Web		

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm — 20

Part No. PE3C7951				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$56.99	$60.99	$65.99	$69.99	$74.99	$59.99	See Web

TFT-402-LF Coax, 50 Ohm — 21

Part No. PE3C7983				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$54.99	$57.99	$59.99	$61.99	$63.99	$56.99	See Web

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm — 22

Part No. PE3C7821				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$79.99	$84.99	$88.99	$92.99	$97.99	$82.99	See Web

SPP-250-LLPL Coax, 50 Ohm — 23

Part No. PE3C5841				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$113.99	$119.99	$125.99	$131.99	$137.99	$117.99	See Web

4.1/9.5 MINI DIN MALE TO 4.1/9.5 MINI DIN FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm — 24

Part No. PE3C7822				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$82.99	$86.99	$90.99	$95.99	$99.99	$85.99	See Web

4.1/9.5 MINI DIN MALE TO 4.3-10 MALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8226				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			25
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.99	$68.99	$73.99	$77.99	$82.99	$67.99	See Web	
Part No. PE3C8228				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			26
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.99	$69.99	$74.99	$78.99	$83.99	$68.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8280				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			27
12"	24"	36"	48"	60"	50CM	Custom Len.	
$57.99	$59.99	$61.99	$64.99	$66.99	$58.99	See Web	
Part No. PE3C8282				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			28
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.99	$65.99	$68.99	$70.99	$72.99	$64.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

4.1/9.5 MINI DIN MALE TO 4.3-10 MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8227				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			29
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.99	$69.99	$74.99	$78.99	$83.99	$68.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8281				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			30
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.99	$65.99	$68.99	$70.99	$72.99	$64.99	See Web	

4.1/9.5 MINI DIN MALE TO 4.3-10 FEMALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8224				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			31
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.99	$68.99	$73.99	$77.99	$82.99	$67.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8278				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			32
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.99	$64.99	$66.99	$69.99	$71.99	$63.99	See Web	

4.1/9.5 MINI DIN MALE TO 4.3-10 FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8225				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			33
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.99	$69.99	$74.99	$78.99	$83.99	$68.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8279				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			34
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.99	$65.99	$68.99	$70.99	$72.99	$64.99	See Web	

4.1/9.5 MINI DIN MALE TO 7/16 DIN MALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8233				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			35
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$64.99	$68.99	$73.99	$77.99	$62.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8287				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			36
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$59.99	$62.99	$64.99	$67.99	$59.99	See Web	

4.1/9.5 MINI DIN MALE TO 7/16 DIN MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8234				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			37
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.99	$65.99	$65.99	$65.99	$65.99	$65.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8288				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			38
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.99	$65.99	$68.99	$70.99	$72.99	$64.99	See Web	

4.1/9.5 MINI DIN MALE TO 7/16 DIN FEMALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8231				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			39
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$64.99	$68.99	$73.99	$77.99	$62.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8285				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			40
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$59.99	$62.99	$64.99	$67.99	$59.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5854				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			41
12"	24"	36"	48"	60"	50CM	Custom Len.	
$113.99	$119.99	$125.99	$131.99	$137.99	$117.99	See Web	

4.1/9.5 MINI DIN MALE TO 7/16 DIN FEMALE 4 HOLE FLANGE

SEE MOUNTING HOLE SECTION ON PAGE 419



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8232				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			42
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$65.99	$69.99	$74.99	$78.99	$63.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8286				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			43
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$61.99	$63.99	$65.99	$68.99	$60.99	See Web	

4.1/9.5 MINI DIN MALE TO N MALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8239				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			44
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$62.99	$66.99	$71.99	$75.99	$60.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8293				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			45
12"	24"	36"	48"	60"	50CM	Custom Len.	
$56.99	$58.99	$60.99	$62.99	$65.99	$57.99	See Web	

4.1/9.5 MINI DIN MALE TO N MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8240				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			46
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$64.99	$68.99	$73.99	$77.99	$62.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8294				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			47
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$59.99	$62.99	$64.99	$67.99	$59.99	See Web	

4.1/9.5 MINI DIN MALE TO N FEMALE



Low PIM Flexible Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3W07481				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			48
24"	36"	48"	60"	150CM	200CM	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

***Coax Performance at 1 GHz** **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

TFT-402 Coax, 50 Ohm

Part No. PE3C8237				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			49
12"	24"	36"	48"	60"	50CM	Custom Len.	
$56.99	$60.99	$65.99	$69.99	$74.99	$59.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8291				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			50
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.99	$57.99	$59.99	$61.99	$63.99	$56.99	See Web	

4.1/9.5 MINI DIN MALE TO N FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8238				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			51
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$62.99	$66.99	$71.99	$75.99	$60.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8292				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			52
12"	24"	36"	48"	60"	50CM	Custom Len.	
$56.99	$58.99	$60.99	$62.99	$65.99	$57.99	See Web	

4.1/9.5 MINI DIN MALE TO QMA MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5866				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			53
12"	24"	36"	48"	60"	50CM	Custom Len.	
$98.99	$105.99	$113.99	$119.99	$125.99	$103.99	See Web	

4.1/9.5 MINI DIN MALE TO QMA MALE RIGHT ANGLE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5872				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			54
12"	24"	36"	48"	60"	50CM	Custom Len.	
$101.99	$109.99	$115.99	$123.99	$127.99	$105.99	See Web	

4.1/9.5 MINI DIN MALE TO QMA FEMALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5860				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			55
12"	24"	36"	48"	60"	50CM	Custom Len.	
$94.99	$101.99	$107.99	$115.99	$121.99	$98.99	See Web	

4.1/9.5 MINI DIN MALE TO SMA MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5885				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			56
12"	24"	36"	48"	60"	50CM	Custom Len.	
$89.99	$96.99	$103.99	$111.99	$117.99	$93.99	See Web	

4.1/9.5 MINI DIN MALE TO SMA MALE RIGHT ANGLE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5890				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			57
12"	24"	36"	48"	60"	50CM	Custom Len.	
$91.99	$98.99	$105.99	$113.99	$119.99	$95.99	See Web	

4.1/9.5 MINI DIN MALE TO SMA FEMALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5879				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			58
12"	24"	36"	48"	60"	50CM	Custom Len.	
$90.99	$97.99	$105.99	$111.99	$119.99	$94.99	See Web	

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO 4.1/9.5 MINI DIN MALE RIGHT ANGLE



Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7823				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		59
12"	24"	36"	48"	60"	50CM	Custom Len.	
$86.99	$90.99	$94.99	$99.99	$103.99	$88.99	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5852				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			60
12"	24"	36"	48"	60"	50CM	Custom Len.	
$133.99	$139.99	$147.99	$153.99	$161.99	$137.99	See Web	
Part No. PE3C6172				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	61
12"	24"	36"	48"	60"	50CM	Custom Len.	
$83.99	$90.99	$97.99	$105.99	$111.99	$87.99	See Web	

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO 4.1/9.5 MINI DIN FEMALE



Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7824				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		62
12"	24"	36"	48"	60"	50CM	Custom Len.	
$84.99	$89.99	$93.99	$97.99	$103.99	$87.99	See Web	

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO 4.1/9.5 MINI DIN FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7825				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		63
12"	24"	36"	48"	60"	50CM	Custom Len.	
$88.99	$92.99	$96.99	$101.99	$105.99	$90.99	See Web	

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO 4.3-10 MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5846				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			64
12"	24"	36"	48"	60"	50CM	Custom Len.	
$121.99	$127.99	$133.99	$139.99	$147.99	$123.99	See Web	
Part No. PE3C6173				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	65
12"	24"	36"	48"	60"	50CM	Custom Len.	
$79.99	$86.99	$92.99	$99.99	$107.99	$83.99	See Web	

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO 4.3-10 FEMALE



Low PIM Flexible Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5950				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			66
12"	24"	36"	48"	60"	50CM	Custom Len.	
$123.99	$131.99	$137.99	$145.99	$151.99	$129.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO 7/16 DIN MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5848				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			67
12"	24"	36"	48"	60"	50CM	Custom Len.	
$123.99	$131.99	$137.99	$145.99	$151.99	$129.99	See Web	
Part No. PE3C6187				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	68
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.99	$81.99	$88.99	$95.99	$103.99	$79.99	See Web	

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO N MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5849				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			69
12"	24"	36"	48"	60"	50CM	Custom Len.	
$117.99	$121.99	$129.99	$135.99	$143.99	$121.99	See Web	
Part No. PE3C6218				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	70
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.99	$78.99	$85.99	$92.99	$99.99	$76.99	See Web	

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO N MALE RIGHT ANGLE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6234				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	71
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.99	$81.99	$88.99	$95.99	$103.99	$79.99	See Web	

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO QMA MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5850				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			72
12"	24"	36"	48"	60"	50CM	Custom Len.	
$113.99	$119.99	$125.99	$131.99	$137.99	$117.99	See Web	

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO SMA MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5851				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			73
12"	24"	36"	48"	60"	50CM	Custom Len.	
$103.99	$109.99	$117.99	$123.99	$129.99	$107.99	See Web	

4.1/9.5 MINI DIN FEMALE TO 4.3-10 MALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8222				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			74
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$65.99	$69.99	$74.99	$78.99	$63.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8277				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			75
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$61.99	$63.99	$65.99	$68.99	$60.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5840				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			76
12"	24"	36"	48"	60"	50CM	Custom Len.	
$113.99	$119.99	$125.99	$131.99	$137.99	$117.99	See Web	

4.1/9.5 MINI DIN FEMALE TO 4.3-10 MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8216				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			77
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$65.99	$69.99	$74.99	$78.99	$63.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8276				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			78
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$61.99	$63.99	$65.99	$68.99	$60.99	See Web	

4.1/9.5 MINI DIN FEMALE TO 7/16 DIN MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5842				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			79
12"	24"	36"	48"	60"	50CM	Custom Len.	
$117.99	$121.99	$129.99	$135.99	$143.99	$121.99	See Web	

4.1/9.5 MINI DIN FEMALE TO 7/16 DIN MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8230				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			80
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$65.99	$69.99	$74.99	$78.99	$63.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8284				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			81
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$61.99	$63.99	$65.99	$68.99	$60.99	See Web	

4.1/9.5 MINI DIN FEMALE TO N MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8236				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			82
12"	24"	36"	48"	60"	50CM	Custom Len.	
$55.99	$60.99	$63.99	$68.99	$72.99	$58.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8290				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			83
12"	24"	36"	48"	60"	50CM	Custom Len.	
$53.99	$55.99	$58.99	$60.99	$62.99	$54.99	See Web	

4.3-10 MALE TO 4.3-10 MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6175				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	84
12"	24"	36"	48"	60"	50CM	Custom Len.	
$80.99	$87.99	$94.99	$101.99	$109.99	$84.99	See Web	
Part No. PE3C6178				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	85
12"	24"	36"	48"	60"	50CM	Custom Len.	
$80.99	$87.99	$94.99	$101.99	$109.99	$84.99	See Web	
Part No. PE3C6179				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	86
12"	24"	36"	48"	60"	50CM	Custom Len.	
$77.99	$84.99	$91.99	$98.99	$105.99	$82.99	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C6437				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			87
12"	24"	36"	48"	60"	50CM	Custom Len.	
$80.99	$82.99	$85.99	$87.99	$90.99	$81.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

SPF-250 Coax, 50 Ohm

Part No. PE3C6605				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			88
12"	24"	36"	50CM	100CM	150CM	Custom Len.	
$80.99	$82.99	$85.99	$81.99	$86.99	$90.99	See Web	

4.3-10 MALE TO 4.3-10 MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7953				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			89
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.99	$77.99	$82.99	$86.99	$91.99	$71.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C7985				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			90
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.99	$71.99	$73.99	$76.99	$78.99	$68.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6176				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	91
12"	24"	36"	48"	60"	50CM	Custom Len.	
$79.99	$86.99	$92.99	$99.99	$107.99	$83.99	See Web	

Part No. PE3C6180				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	92
12"	24"	36"	48"	60"	50CM	Custom Len.	
$79.99	$86.99	$92.99	$99.99	$107.99	$83.99	See Web	

4.3-10 MALE TO 4.3-10 FEMALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7954				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			93
12"	24"	36"	48"	60"	50CM	Custom Len.	
$71.99	$76.99	$80.99	$85.99	$89.99	$70.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C7986				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			94
12"	24"	36"	48"	60"	50CM	Custom Len.	
$67.99	$70.99	$72.99	$74.99	$77.99	$66.99	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7828				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		95
12"	24"	36"	48"	60"	50CM	Custom Len.	
$82.99	$86.99	$90.99	$96.99	$101.99	$85.99	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6174				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	96
12"	24"	36"	48"	60"	50CM	Custom Len.	
$80.99	$87.99	$94.99	$101.99	$109.99	$84.99	See Web	

Part No. PE3C6229				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	97
12"	24"	36"	48"	60"	50CM	Custom Len.	
$80.99	$87.99	$94.99	$101.99	$109.99	$84.99	See Web	

4.3-10 MALE TO 4.3-10 FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7955				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			98
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.99	$77.99	$82.99	$86.99	$91.99	$71.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C7987				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			99
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.99	$71.99	$73.99	$76.99	$78.99	$68.99	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7829				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		1
12"	24"	36"	48"	60"	50CM	Custom Len.	
$84.99	$88.99	$93.99	$97.99	$101.99	$87.99	See Web	

4.3-10 MALE TO 4.3-10 FEMALE 4 HOLE FLANGE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7830				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		2
12"	24"	36"	48"	60"	50CM	Custom Len.	
$80.99	$84.99	$89.99	$93.99	$97.99	$83.99	See Web	

4.3-10 MALE TO 7/16 DIN MALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8247				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			3
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.99	$67.99	$71.99	$76.99	$80.99	$65.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8301				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			4
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$63.99	$65.99	$67.99	$70.99	$62.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6184				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	5
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.99	$80.99	$87.99	$93.99	$101.99	$77.99	See Web	

Part No. PE3C6186				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	6
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.99	$80.99	$87.99	$93.99	$101.99	$77.99	See Web	

4.3-10 MALE TO 7/16 DIN MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8248				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			7
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.99	$73.99	$77.99	$82.99	$86.99	$71.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8302				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			8
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.99	$69.99	$71.99	$73.99	$76.99	$68.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6236				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	9
12"	24"	36"	48"	60"	50CM	Custom Len.	
$79.99	$86.99	$92.99	$99.99	$107.99	$83.99	See Web	

Part No. PE3C6238				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	10
12"	24"	36"	48"	60"	50CM	Custom Len.	
$79.99	$86.99	$92.99	$99.99	$107.99	$83.99	See Web	

4.3-10 MALE TO 7/16 DIN FEMALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8245				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			11
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.99	$67.99	$71.99	$76.99	$80.99	$65.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8299				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			12
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$63.99	$65.99	$67.99	$70.99	$62.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5853				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			13
12"	24"	36"	48"	60"	50CM	Custom Len.	
$113.99	$119.99	$125.99	$131.99	$137.99	$117.99	See Web	

Part No. PE3C6230				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	14
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.99	$80.99	$87.99	$93.99	$101.99	$77.99	See Web	
Part No. PE3C6232				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	15
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.99	$80.99	$87.99	$93.99	$101.99	$77.99	See Web	

SPO-375 Coax, 50 Ohm

Part No. PE3C6501				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			16
12"	24"	36"	48"	60"	50CM	Custom Len.	
$81.99	$84.99	$88.99	$91.99	$95.99	$83.99	See Web	

SPF-375 Coax, 50 Ohm

Part No. PE3C6507				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.435" dia.			17
12"	24"	36"	48"	60"	50CM	Custom Len.	
$81.99	$85.99	$90.99	$95.99	$101.99	$84.99	See Web	

4.3-10 MALE TO 7/16 DIN FEMALE 4 HOLE FLANGE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8246				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			18
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.99	$68.99	$73.99	$77.99	$82.99	$67.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8300				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			19
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.99	$64.99	$66.99	$69.99	$71.99	$63.99	See Web	

4.3-10 MALE TO N MALE



Low Loss Flexible Cable Assemblies

LMR-240-UF Coax, 50 Ohm

Part No. PE3C7907				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft		20
12"	24"	36"	48"	60"	50CM	Custom Len.	
$61.99	$61.99	$63.99	$64.99	$65.99	$60.99	See Web	

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8259				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			21
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$65.99	$69.99	$74.99	$78.99	$63.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8313				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			22
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$61.99	$63.99	$65.99	$68.99	$60.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6221				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	23
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.99	$77.99	$84.99	$91.99	$97.99	$75.99	See Web	
Part No. PE3C6223				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	24
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.99	$77.99	$84.99	$91.99	$97.99	$75.99	See Web	

4.3-10 MALE TO N MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8260				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			25
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.99	$67.99	$71.99	$76.99	$80.99	$65.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8314				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			26
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$63.99	$65.99	$67.99	$70.99	$62.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6228				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	27
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.99	$80.99	$87.99	$93.99	$101.99	$77.99	See Web	
Part No. PE3C6243				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	28
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.99	$80.99	$87.99	$93.99	$101.99	$77.99	See Web	

4.3-10 MALE TO N FEMALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8257				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			29
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$64.99	$68.99	$73.99	$77.99	$62.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8311				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			30
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$59.99	$62.99	$64.99	$67.99	$59.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6220				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	31
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.99	$77.99	$84.99	$91.99	$97.99	$75.99	See Web	
Part No. PE3C6225				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	32
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.99	$77.99	$84.99	$91.99	$97.99	$75.99	See Web	

4.3-10 MALE TO N FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8258				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			33
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$65.99	$69.99	$74.99	$78.99	$63.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8312				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			34
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$61.99	$63.99	$65.99	$68.99	$60.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6219				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	35
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.99	$77.99	$84.99	$91.99	$97.99	$75.99	See Web	
Part No. PE3C6226				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	36
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.99	$77.99	$84.99	$91.99	$97.99	$75.99	See Web	

4.3-10 MALE TO QMA MALE



Low PIM Flexible Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5865				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	37
12"	24"	36"	48"	60"	50CM	Custom Len.	
$98.99	$105.99	$113.99	$119.99	$125.99	$103.99	See Web	

4.3-10 MALE TO QMA MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5871				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	38
12"	24"	36"	48"	60"	50CM	Custom Len.	
$101.99	$109.99	$115.99	$123.99	$127.99	$105.99	See Web	

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

4.3-10 MALE TO QMA FEMALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5859				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			39
12"	24"	36"	48"	60"	50CM	Custom Len.	
$94.99	$101.99	$107.99	$115.99	$121.99	$98.99	See Web	

4.3-10 MALE TO SMA MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5884				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			40
12"	24"	36"	48"	60"	50CM	Custom Len.	
$89.99	$96.99	$103.99	$111.99	$117.99	$93.99	See Web	
Part No. PE3C6246				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	41
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.99	$71.99	$78.99	$85.99	$92.99	$69.99	See Web	
Part No. PE3C6247				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	42
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.99	$72.99	$79.99	$86.99	$92.99	$69.99	See Web	

4.3-10 MALE TO SMA MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5889				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	43
12"	24"	36"	48"	60"	50CM	Custom Len.	
$91.99	$98.99	$105.99	$113.99	$119.99	$95.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6248				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	44
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.99	$77.99	$84.99	$91.99	$97.99	$75.99	See Web	
Part No. PE3C6250				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	45
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.99	$77.99	$84.99	$91.99	$97.99	$75.99	See Web	

4.3-10 MALE TO SMA FEMALE



Low PIM Flexible Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5878				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	46
12"	24"	36"	48"	60"	50CM	Custom Len.	
$90.99	$97.99	$105.99	$111.99	$119.99	$94.99	See Web	

4.3-10 MALE TO NEX10 MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6263				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	47
12"	24"	36"	48"	60"	50CM	Custom Len.	
$80.99	$86.99	$93.99	$101.99	$107.99	$84.99	See Web	

4.3-10 MALE RIGHT ANGLE TO 4.3-10 MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4147				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			48
12"	24"	36"	48"	60"	50CM	Custom Len.	
$123.99	$129.99	$135.99	$143.99	$149.99	$127.99	See Web	

Standard Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7827				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		49
12"	24"	36"	48"	60"	50CM	Custom Len.	
$83.99	$87.99	$92.99	$96.99	$101.99	$86.99	See Web	

4.3-10 MALE RIGHT ANGLE TO 4.3-10 MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7956				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			50
12"	24"	36"	48"	60"	50CM	Custom Len.	
$76.99	$81.99	$85.99	$90.99	$95.99	$74.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C7988				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			51
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.99	$74.99	$77.99	$79.99	$82.99	$71.99	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7831				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		52
12"	24"	36"	48"	60"	50CM	Custom Len.	
$86.99	$91.99	$95.99	$101.99	$105.99	$89.99	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4146				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			53
12"	24"	36"	48"	60"	50CM	Custom Len.	
$131.99	$137.99	$145.99	$151.99	$159.99	$135.99	See Web	
Part No. PE3C6177				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	54
12"	24"	36"	48"	60"	50CM	Custom Len.	
$83.99	$90.99	$97.99	$105.99	$111.99	$87.99	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C6339				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			55
12"	24"	36"	48"	60"	50CM	Custom Len.	
$78.99	$81.99	$84.99	$86.99	$89.99	$80.99	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C6354				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			56
12"	24"	36"	48"	60"	50CM	Custom Len.	
$79.99	$83.99	$86.99	$89.99	$93.99	$81.99	See Web	

4.3-10 MALE RIGHT ANGLE TO 4.3-10 FEMALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7957				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			57
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.99	$77.99	$82.99	$86.99	$91.99	$71.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C7989				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			58
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.99	$71.99	$73.99	$76.99	$78.99	$68.99	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7832				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		59
12"	24"	36"	48"	60"	50CM	Custom Len.	
$84.99	$89.99	$94.99	$98.99	$103.99	$88.99	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6227				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	60
12"	24"	36"	48"	60"	50CM	Custom Len.	
$81.99	$88.99	$95.99	$103.99	$109.99	$86.99	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C6332				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			61
12"	24"	36"	48"	60"	50CM	Custom Len.	
$77.99	$79.99	$82.99	$85.99	$87.99	$79.99	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C6349				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			62
12"	24"	36"	48"	60"	50CM	Custom Len.	
$78.99	$81.99	$84.99	$88.99	$91.99	$80.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

4.3-10 MALE RIGHT ANGLE TO 4.3-10 FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7958				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			63
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.99	$79.99	$83.99	$88.99	$92.99	$72.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C7990				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			64
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.99	$72.99	$75.99	$77.99	$79.99	$69.99	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7833				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		65
12"	24"	36"	48"	60"	50CM	Custom Len.	
$86.99	$91.99	$95.99	$101.99	$105.99	$89.99	See Web	

4.3-10 MALE RIGHT ANGLE TO 4.3-10 FEMALE 4 HOLE FLANGE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7834				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		66
12"	24"	36"	48"	60"	50CM	Custom Len.	
$83.99	$87.99	$91.99	$96.99	$101.99	$85.99	See Web	

4.3-10 MALE RIGHT ANGLE TO 7/16 DIN MALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8251				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			67
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.99	$68.99	$73.99	$77.99	$82.99	$67.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8305				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			68
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.99	$64.99	$66.99	$69.99	$71.99	$63.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6185				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	69
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.99	$81.99	$88.99	$95.99	$103.99	$79.99	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C6340				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			70
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.99	$73.99	$75.99	$78.99	$80.99	$72.99	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C6355				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			71
12"	24"	36"	48"	60"	50CM	Custom Len.	
$71.99	$74.99	$78.99	$81.99	$84.99	$73.99	See Web	

4.3-10 MALE RIGHT ANGLE TO 7/16 DIN MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8252				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			72
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.99	$74.99	$79.99	$83.99	$88.99	$72.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8306				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			73
12"	24"	36"	48"	60"	50CM	Custom Len.	
$67.99	$70.99	$72.99	$75.99	$77.99	$69.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6237				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	74
12"	24"	36"	48"	60"	50CM	Custom Len.	
$80.99	$87.99	$94.99	$101.99	$107.99	$85.99	See Web	

4.3-10 MALE RIGHT ANGLE TO 7/16 DIN FEMALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8249				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			75
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.99	$68.99	$73.99	$77.99	$82.99	$67.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8303				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			76
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.99	$64.99	$66.99	$69.99	$71.99	$63.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6231				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	77
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.99	$81.99	$88.99	$95.99	$103.99	$79.99	See Web	

4.3-10 MALE RIGHT ANGLE TO 7/16 DIN FEMALE 4 HOLE FLANGE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8250				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			78
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.99	$69.99	$74.99	$78.99	$83.99	$68.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8304				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			79
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.99	$65.99	$68.99	$70.99	$72.99	$64.99	See Web	

4.3-10 MALE RIGHT ANGLE TO N MALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8263				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			80
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.99	$66.99	$71.99	$75.99	$80.99	$65.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8317				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			81
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$62.99	$64.99	$67.99	$69.99	$61.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6222				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	82
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.99	$78.99	$85.99	$92.99	$99.99	$76.99	See Web	

4.3-10 MALE RIGHT ANGLE TO N MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8264				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			83
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.99	$68.99	$73.99	$77.99	$82.99	$67.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8318				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			84
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.99	$64.99	$66.99	$69.99	$71.99	$63.99	See Web	

***Coax Performance at 1 GHz** **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6242				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$75.99	$81.99	$88.99	$95.99	$103.99	$79.99	See Web

85

4.3-10 MALE RIGHT ANGLE TO N FEMALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8261				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$60.99	$65.99	$69.99	$74.99	$78.99	$63.99	See Web

86

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8315				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$59.99	$61.99	$63.99	$65.99	$68.99	$60.99	See Web

87

4.3-10 MALE RIGHT ANGLE TO N FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8262				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$62.99	$66.99	$71.99	$75.99	$80.99	$65.99	See Web

88

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8316				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$60.99	$62.99	$64.99	$67.99	$69.99	$61.99	See Web

89

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6239				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$72.99	$78.99	$85.99	$92.99	$99.99	$76.99	See Web

90

4.3-10 MALE RIGHT ANGLE TO SMA MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6245				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$66.99	$73.99	$79.99	$86.99	$93.99	$70.99	See Web

91

4.3-10 MALE RIGHT ANGLE TO SMA MALE RIGHT ANGLE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6249				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$72.99	$78.99	$85.99	$92.99	$99.99	$76.99	See Web

92

4.3-10 MALE RIGHT ANGLE TO NEX10 MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6262				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$81.99	$88.99	$95.99	$101.99	$109.99	$85.99	See Web

93

4.3-10 FEMALE TO 4.3-10 MALE



Low PIM Flexible Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5833				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$113.99	$119.99	$125.99	$131.99	$137.99	$117.99	See Web

94

4.3-10 FEMALE TO 7/16 DIN MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6233				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$75.99	$82.99	$89.99	$96.99	$103.99	$80.99	See Web

95

SPO-250 Coax, 50 Ohm

Part No. PE3C8501				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.		
7"	18CM	-	-	-	-	Custom Len.
$59.99	$62.99	$64.99	$67.99	$69.99	$61.99	See Web

96

4.3-10 FEMALE TO 7/16 DIN MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8242				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$68.99	$73.99	$77.99	$82.99	$86.99	$71.99	See Web

97

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8296				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$66.99	$69.99	$71.99	$73.99	$76.99	$68.99	See Web

98

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6235				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$81.99	$88.99	$95.99	$103.99	$109.99	$86.99	See Web

99

4.3-10 FEMALE TO N MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6240				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$72.99	$79.99	$86.99	$93.99	$101.99	$77.99	See Web

1

4.3-10 FEMALE TO N MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8254				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$62.99	$67.99	$71.99	$76.99	$80.99	$65.99	See Web

2

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8308				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$60.99	$63.99	$65.99	$67.99	$70.99	$62.99	See Web

3

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6241				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$75.99	$82.99	$89.99	$96.99	$103.99	$80.99	See Web

4

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

SPO-250 Coax, 50 Ohm

Part No. PE3C6337				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$71.99	$73.99	$76.99	$79.99	$81.99	$73.99	See Web

5

SPF-250 Coax, 50 Ohm

Part No. PE3C6352				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$72.99	$75.99	$79.99	$82.99	$85.99	$74.99	See Web

6

4.3-10 FEMALE TO NEX10 MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6264				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$82.99	$89.99	$96.99	$103.99	$111.99	$86.99	See Web

7

4.3-10 FEMALE BULKHEAD TO 7/16 DIN MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8243				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$64.99	$68.99	$73.99	$77.99	$82.99	$67.99	See Web

8

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8297				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$62.99	$64.99	$66.99	$69.99	$71.99	$63.99	See Web

9

4.3-10 FEMALE BULKHEAD TO 7/16 DIN MALE RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8244				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$70.99	$74.99	$79.99	$83.99	$88.99	$72.99	See Web

10

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8298				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$67.99	$70.99	$72.99	$75.99	$77.99	$69.99	See Web

11

4.3-10 FEMALE BULKHEAD TO N MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8255				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$62.99	$66.99	$71.99	$75.99	$80.99	$65.99	See Web

12

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8309				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$60.99	$62.99	$64.99	$67.99	$69.99	$61.99	See Web

13

4.3-10 FEMALE BULKHEAD TO N MALE RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8256				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$64.99	$68.99	$73.99	$77.99	$82.99	$67.99	See Web

14

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8310				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$62.99	$64.99	$66.99	$69.99	$71.99	$63.99	See Web

15

7/16 DIN MALE TO 4.3-10 FEMALE



Low PIM Flexible Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5836				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$117.99	$121.99	$129.99	$135.99	$143.99	$121.99	See Web

16

7/16 DIN MALE TO 7/16 DIN MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE37952				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W
36"	48"	60"	72"	120"	-	Custom Len.
$109.99	$109.99	$111.99	$111.99	$115.99	-	See Web

17

PE-C240 Coax, 50 Ohm

Part No. PE37953				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W
36"	48"	60"	72"	120"	-	Custom Len.
$133.99	$133.99	$135.99	$137.99	$141.99	-	See Web

18

PE-C400 Coax, 50 Ohm

Part No. PE37954				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W
36"	48"	60"	72"	120"	-	Custom Len.
$179.99	$181.99	$183.99	$183.99	$191.99	-	See Web

19

PE-C600 Coax, 50 Ohm

Part No. PE37955				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.7 dB/100ft	900 W
36"	48"	60"	72"	120"	-	Custom Len.
$215.99	$205.99	$209.99	$213.99	$225.99	-	See Web

20

LMR-400 Coax, 50 Ohm

Part No. PE3W03530				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$111.99	$111.99	$113.99	$115.99	$117.99	$111.99	See Web

21

Low PIM Formable Cable Assemblies

PE-SR401FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2013				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.276" dia.		
100CM	200CM	-	-	-	-	Custom Len.
$221.99	$255.99	-	-	-	-	See Web

22

PE-SR402FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2003				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.161" dia.		
100CM	200CM	-	-	-	-	Custom Len.
Call	$187.99	-	-	-	-	See Web

23

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6181				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$71.99	$78.99	$85.99	$92.99	$99.99	$75.99	See Web

24

SPP-375-LLPL Coax, 50 Ohm

Part No. PE3C8518				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.402" dia.		
7"	18CM	-	-	-	-	Custom Len.
$52.99	$61.99	$69.99	$77.99	$85.99	$58.99	See Web

25

Standard Formable Cable Assemblies

PE-SR401FL Coax, 50 Ohm

Part No. PE36140				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W
12"	24"	36"	48"	60"	72"	Custom Len.
$373.99	$391.99	$409.99	$427.99	$445.99	$463.99	See Web

26

PE-SR402FL Coax, 50 Ohm

Part No. PE36144				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W
12"	24"	36"	48"	60"	72"	Custom Len.
$357.99	$365.99	$375.99	$383.99	$391.99	$401.99	See Web

27

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE35283				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W
12"	24"	36"	48"	60"	-	Custom Len.
$303.99	$307.99	$309.99	$313.99	$315.99	-	See Web

28

See Our Website For Current Pricing & Real-Time Stock Availability!

***Coax Performance at 1 GHz** **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

For our complete selection of cable assemblies, please visit our website

RG58C/U Coax, 50 Ohm

Part No. PE3183				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	29
12"	24"	36"	48"	60"	72"	Custom Len.	
$291.99	$291.99	$291.99	$293.99	$293.99	$295.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3189				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		30
12"	24"	36"	48"	60"	72"	Custom Len.	
$129.99	$135.99	$143.99	$149.99	$157.99	$163.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3199				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	9 dB/100ft	190 W	31
12"	24"	36"	48"	60"	72"	Custom Len.	
$303.99	$305.99	$307.99	$309.99	$311.99	$313.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3185				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	32
12"	24"	36"	48"	60"	72"	Custom Len.	
$321.99	$331.99	$339.99	$369.99	$357.99	$365.99	See Web	

RG217/U Coax, 50 Ohm

Part No. PE36134				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.	5.8 dB/100ft	260 W	33
12"	24"	36"	48"	60"	72"	Custom Len.	
$389.99	$395.99	$399.99	$405.99	$411.99	$417.99	See Web	

RG218/U Coax, 50 Ohm

Part No. PE35900				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.87" dia.	3.8 dB/100ft	560 W	34
12"	24"	36"	48"	60"	72"	Custom Len.	
$433.99	$447.99	$461.99	$475.99	$520.00	$505.00	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3192				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	35
12"	24"	36"	48"	60"	72"	Custom Len.	
$119.99	$121.99	$125.99	$129.99	$133.99	$135.99	See Web	

RG225/U Coax, 50 Ohm

Part No. PE36136				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	36
12"	24"	36"	48"	60"	72"	Custom Len.	
$337.99	$377.99	$417.99	$457.99	$497.99	$540.00	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3205				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	37
12"	24"	36"	48"	60"	72"	Custom Len.	
$335.99	$201.99	$221.99	$243.99	$263.99	$283.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34360				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	38
12"	24"	36"	48"	60"	72"	Custom Len.	
$131.99	$139.99	$147.99	$157.99	$165.99	$173.99	See Web	

Standard Semi-Rigid Cable Assemblies

RG401/U Coax, 50 Ohm

Part No. PE36138				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	39
12"	24"	36"	48"	60"	72"	Custom Len.	
$387.99	$415.99	$441.99	$467.99	$493.99	Call	See Web	

RG402/U Coax, 50 Ohm

Part No. PE36142				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	40
12"	24"	36"	48"	60"	72"	Custom Len.	
$363.99	$371.99	$381.99	$389.99	$397.99	$407.99	See Web	

7/16 DIN MALE TO
7/16 DIN MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE37956				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	41
36"	48"	60"	72"	120"	-	Custom Len.	
$103.99	$103.99	$105.99	$105.99	$109.99	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE37957				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	42
36"	48"	60"	72"	120"	-	Custom Len.	
$159.99	$161.99	$161.99	$163.99	$167.99	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE37958				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	43
36"	48"	60"	72"	120"	-	Custom Len.	
$199.99	$201.99	$203.99	$205.99	$211.99	-	See Web	

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7960				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			44
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.99	$73.99	$77.99	$82.99	$86.99	$67.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C7992				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			45
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.99	$66.99	$69.99	$71.99	$74.99	$63.99	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7836				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		46
12"	24"	36"	48"	60"	50CM	Custom Len.	
$81.99	$86.99	$90.99	$94.99	$99.99	$84.99	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6188				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	47
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.99	$81.99	$88.99	$95.99	$103.99	$79.99	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C8493				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			48
7"	18CM	-	-	-	-	Custom Len.	
$61.99	$65.99	$68.99	$71.99	$74.99	$63.99	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C8510				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			49
7"	18CM	-	-	-	-	Custom Len.	
$61.99	$63.99	$65.99	$68.99	$70.99	$62.99	See Web	

Standard Flexible Cable Assemblies

RG214/U Coax, 50 Ohm

Part No. PE38584				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	50
12"	24"	36"	48"	60"	-	Custom Len.	
$349.99	$357.99	$365.99	$375.99	$383.99	-	See Web	

RG217/U Coax, 50 Ohm

Part No. PE37600				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.	5.8 dB/100ft	260 W	51
12"	24"	36"	48"	60"	-	Custom Len.	
$435.99	$441.99	$447.99	$451.99	$485.99	-	See Web	

RG393/U Coax, 50 Ohm

Part No. PE36657				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W	52
12"	24"	36"	48"	60"	-	Custom Len.	
$383.99	$403.99	$399.99	$419.99	$465.99	-	See Web	

PE-1/2 Helical Coax, 50 Ohm

Part No. PE37973				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.54" dia.			53
36"	72"	-	-	-	-	Custom Len.	
Call	Call	-	-	-	-	See Web	

7/16 DIN MALE TO
7/16 DIN FEMALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE37960				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	54
36"	48"	60"	72"	120"	-	Custom Len.	
$103.99	$103.99	$105.99	$105.99	$109.99	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE37961				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	55
36"	48"	60"	72"	120"	-	Custom Len.	
$151.99	$153.99	$153.99	$155.99	$159.99	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE37962				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	56
36"	48"	60"	72"	120"	-	Custom Len.	
$193.99	$195.99	$195.99	$197.99	$203.99	-	See Web	

PE-C600 Coax, 50 Ohm

Part No. PE37963				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.7 dB/100ft	900 W	57
36"	48"	60"	72"	120"	-	Custom Len.	
$211.99	$213.99	$217.99	$219.99	$231.99	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

Low PIM Formable Cable Assemblies

PE-SR401FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2015				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.276" dia.			58
100CM	200CM	-	-	-	-	Custom Len.	
$221.99	$255.99	-	-	-	-	See Web	

PE-SR402FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2004				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.			59
100CM	200CM	-	-	-	-	Custom Len.	
Call	Call	-	-	-	-	See Web	

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7961					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.16" dia.			60
12"	24"	36"	48"	60"	50CM	Custom Len.		
$62.99	$67.99	$71.99	$76.99	$80.99	$61.99	See Web		

TFT-402-LF Coax, 50 Ohm

Part No. PE3C7993					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.16" dia.			61
12"	24"	36"	48"	60"	50CM	Custom Len.		
$59.99	$60.99	$63.99	$65.99	$68.99	$58.99	See Web		

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7837					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.303" dia.	5.85 dB/100ft		62
12"	24"	36"	48"	60"	50CM	Custom Len.		
$74.99	$79.99	$83.99	$87.99	$91.99	$77.99	See Web		

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5855					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.28" dia.			63
12"	24"	36"	48"	60"	50CM	Custom Len.		
$117.99	$121.99	$129.99	$135.99	$143.99	$121.99	See Web		

Part No. PE3C6182					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.28" dia.	5.5 dB/100ft	650 W	64
12"	24"	36"	48"	60"	50CM	Custom Len.		
$69.99	$76.99	$82.99	$89.99	$96.99	$73.99	See Web		

SPP-375-LLPL Coax, 50 Ohm

Part No. PE3C8519					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.402" dia.			65
7"	18CM	-	-	-	-	Custom Len.		
$52.99	$61.99	$69.99	$77.99	$85.99	$58.99	See Web		

SPO-250 Coax, 50 Ohm

Part No. PE3C8511					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.303" dia.			66
7"	18CM	-	-	-	-	Custom Len.		
$55.99	$57.99	$59.99	$62.99	$64.99	$56.99	See Web		

SPO-375 Coax, 50 Ohm

Part No. PE3C6503					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.43" dia.			67
12"	24"	36"	48"	60"	50CM	Custom Len.		
$81.99	$84.99	$88.99	$91.99	$95.99	$83.99	See Web		

SPF-250 Coax, 50 Ohm

Part No. PE3C8494					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.303" dia.			68
7"	18CM	-	-	-	-	Custom Len.		
$55.99	$58.99	$62.99	$65.99	$68.99	$57.99	See Web		

SPF-375 Coax, 50 Ohm

Part No. PE3C6509					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.435" dia.			69
12"	24"	36"	48"	60"	50CM	Custom Len.		
$81.99	$85.99	$90.99	$95.99	$101.99	$84.99	See Web		

Standard Flexible Cable Assemblies

RG393/U Coax, 50 Ohm

Part No. PE37450					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.39" dia.	8.8 dB/100ft	1,700 W	70
12"	24"	36"	48"	60"	-	Custom Len.		
$347.99	$367.99	$385.99	$405.99	$451.99	-	See Web		

PE-1/2 Helical Coax, 50 Ohm

Part No. PE37972					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.54" dia.			71
36"	72"	-	-	-	-	Custom Len.		
Call	Call	-	-	-	-	See Web		

7/16 DIN MALE TO
7/16 DIN FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7838				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		72
12"	50CM	24"	36"	48"	60"	Custom Len.	
$89.99	$92.99	$93.99	$97.99	$103.99	$107.99	See Web	

7/16 DIN MALE TO
7/16 DIN FEMALE 4 HOLE FLANGE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7962				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			73
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.99	$68.99	$73.99	$77.99	$82.99	$62.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C7994				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			74
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$62.99	$64.99	$67.99	$69.99	$59.99	See Web	

7/16 DIN MALE TO
N MALE



Low Loss Flexible Cable Assemblies

LMR-400-UF Coax, 50 Ohm

Part No. PE3W03271				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	5 dB/100ft		75
12"	24"	36"	48"	60"	50CM	Custom Len.	
$117.99	$119.99	$123.99	$125.99	$127.99	$119.99	See Web	

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8269				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			76
12"	24"	36"	48"	60"	50CM	Custom Len.	
$56.99	$60.99	$65.99	$69.99	$74.99	$59.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8323				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			77
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.99	$57.99	$59.99	$61.99	$63.99	$56.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6192				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	78
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.99	$73.99	$79.99	$86.99	$93.99	$70.99	See Web	

SPP-375-LLPL Coax, 50 Ohm

Part No. PE3C8444				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.402" dia.			79
7"	18CM	-	-	-	-	Custom Len.	
$50.99	$58.99	$66.99	$75.99	$83.99	$55.99	See Web	

SPO-375 Coax, 50 Ohm

Part No. PE3W11883				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			80
7"	18CM	-	-	-	-	Custom Len.	
$48.19	$51.99	$54.99	$56.99	$59.99	$49.99	See Web	

Standard Semi-Rigid Cable Assemblies

RG401/U Coax, 50 Ohm

Part No. PE36174				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	1,400 W	81
12"	24"	36"	48"	60"	72"	Custom Len.	
$271.99	$297.99	$323.99	$349.99	$377.99	Call	See Web	

7/16 DIN MALE TO
N MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8270				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			82
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$62.99	$67.99	$71.99	$76.99	$61.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8324				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			83
12"	24"	36"	48"	60"	50CM	Custom Len.	
$56.99	$59.99	$60.99	$63.99	$65.99	$58.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

***Coax Performance at 1 GHz** **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6193				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	84
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.99	$76.99	$82.99	$89.99	$96.99	$73.99	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C6343				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			85
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.99	$67.99	$70.99	$72.99	$75.99	$66.99	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C6358				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			86
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.99	$69.99	$72.99	$75.99	$79.99	$68.99	See Web	

7/16 DIN MALE TO N FEMALE



Low PIM Flexible Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4133				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	87
12"	24"	36"	48"	60"	50CM	Custom Len.	
$115.99	$123.99	$127.99	$135.99	$141.99	$119.99	See Web	

TFT-402 Coax, 50 Ohm

Part No. PE3C8267				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			88
12"	24"	36"	48"	60"	50CM	Custom Len.	
$55.99	$60.99	$63.99	$68.99	$72.99	$58.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8321				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			89
12"	24"	36"	48"	60"	50CM	Custom Len.	
$53.99	$55.99	$58.99	$60.99	$62.99	$54.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6190				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	90
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.99	$73.99	$79.99	$86.99	$93.99	$70.99	See Web	

SPP-375-LLPL Coax, 50 Ohm

Part No. PE3C8516				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.402" dia.			91
7"	18CM	-	-	-	-	Custom Len.	
$50.99	$58.99	$66.99	$75.99	$83.99	$55.99	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C8502				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			92
7"	18CM	-	-	-	-	Custom Len.	
$53.99	$55.99	$58.99	$60.99	$62.99	$55.99	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C8485				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			93
7"	18CM	-	-	-	-	Custom Len.	
$54.99	$57.99	$60.99	$63.99	$66.99	$56.99	See Web	

SPF-375 Coax, 50 Ohm

Part No. PE3C8497				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.435" dia.			94
7"	18CM	-	-	-	-	Custom Len.	
$45.99	$49.99	$53.99	$57.99	$61.99	$48.59	See Web	

7/16 DIN MALE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8268				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			95
12"	24"	36"	48"	60"	50CM	Custom Len.	
$56.99	$60.99	$65.99	$69.99	$74.99	$59.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8322				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			96
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.99	$57.99	$59.99	$61.99	$63.99	$56.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6191				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	97
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.99	$73.99	$79.99	$86.99	$93.99	$70.99	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C8503				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			98
7"	18CM	-	-	-	-	Custom Len.	
$53.99	$55.99	$58.99	$60.99	$62.99	$55.99	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C8486				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			99
7"	18CM	-	-	-	-	Custom Len.	
$54.99	$57.99	$60.99	$63.99	$66.99	$56.99	See Web	

7/16 DIN MALE TO QMA MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5867				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			1
12"	24"	36"	48"	60"	50CM	Custom Len.	
$103.99	$109.99	$117.99	$123.99	$129.99	$107.99	See Web	

7/16 DIN MALE TO QMA MALE RIGHT ANGLE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5873				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			2
12"	24"	36"	48"	60"	50CM	Custom Len.	
$105.99	$113.99	$119.99	$125.99	$131.99	$111.99	See Web	

7/16 DIN MALE TO QMA FEMALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5861				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			3
12"	24"	36"	48"	60"	50CM	Custom Len.	
$98.99	$105.99	$113.99	$119.99	$125.99	$103.99	See Web	

7/16 DIN MALE TO SC MALE



Standard Flexible Cable Assemblies

RG393/U Coax, 50 Ohm

Part No. PE37497				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W	4
12"	24"	36"	48"	60"	50CM	Custom Len.	
$255.99	$275.99	$293.99	$313.99	$333.99	$267.99	See Web	

7/16 DIN MALE TO SMA MALE



Low PIM Flexible Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5886				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	5
12"	24"	36"	48"	60"	50CM	Custom Len.	
$94.99	$101.99	$107.99	$115.99	$121.99	$98.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6194				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	6
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$67.99	$74.99	$80.99	$87.99	$64.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

7/16 DIN MALE TO SMA MALE RIGHT ANGLE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5891				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			7
12"	24"	36"	48"	60"	50CM	Custom Len.	
$95.99	$103.99	$109.99	$117.99	$121.99	$101.99	See Web	

Part No. PE3C6195				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	8
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.99	$73.99	$79.99	$86.99	$93.99	$70.99	See Web	

7/16 DIN MALE TO SMA FEMALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5880				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			9
12"	24"	36"	48"	60"	50CM	Custom Len.	
$94.99	$101.99	$109.99	$115.99	$121.99	$99.99	See Web	

7/16 DIN MALE RIGHT ANGLE TO 7/16 DIN MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4131				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			10
12"	24"	36"	48"	60"	50CM	Custom Len.	
$133.99	$141.99	$147.99	$155.99	$161.99	$139.99	See Web	

7/16 DIN MALE RIGHT ANGLE TO 7/16 DIN MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7963				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			11
12"	24"	36"	48"	60"	50CM	Custom Len.	
$76.99	$81.99	$85.99	$90.99	$95.99	$74.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C7995				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			12
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.99	$76.99	$78.99	$81.99	$83.99	$72.99	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7839				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		13
12"	24"	36"	48"	60"	50CM	Custom Len.	
$86.99	$90.99	$94.99	$99.99	$103.99	$88.99	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4144				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			14
12"	24"	36"	48"	60"	50CM	Custom Len.	
$149.99	$155.99	$161.99	$169.99	$175.99	$153.99	See Web	

Part No. PE3C6189				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	15
12"	24"	36"	48"	60"	50CM	Custom Len.	
$83.99	$90.99	$97.99	$105.99	$111.99	$87.99	See Web	

7/16 DIN MALE RIGHT ANGLE TO 7/16 DIN FEMALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7964				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			16
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.99	$73.99	$77.99	$82.99	$86.99	$67.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C7996				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			17
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.99	$67.99	$70.99	$72.99	$75.99	$64.99	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7840				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		18
12"	50CM	24"	36"	48"	60"	Custom Len.	
$80.99	$83.99	$84.99	$89.99	$93.99	$97.99	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6183				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	19
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.99	$81.99	$88.99	$95.99	$103.99	$79.99	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C8495				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			20
7"	18CM	-	-	-	-	Custom Len.	
$60.99	$64.99	$67.99	$70.99	$73.99	$62.99	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C8512				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			21
7"	18CM	-	-	-	-	Custom Len.	
$60.99	$62.99	$64.99	$67.99	$69.99	$61.99	See Web	

7/16 DIN MALE RIGHT ANGLE TO 7/16 DIN FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7841				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		22
12"	24"	36"	48"	60"	50CM	Custom Len.	
$95.99	$99.99	$103.99	$107.99	$113.99	$97.99	See Web	

7/16 DIN MALE RIGHT ANGLE TO 7/16 DIN FEMALE 4 HOLE FLANGE

SEE MOUNTING HOLE SECTION ON PAGE 419



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7965				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			23
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.99	$74.99	$78.99	$83.99	$87.99	$68.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C7997				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			24
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.99	$69.99	$71.99	$74.99	$76.99	$66.99	See Web	

7/16 DIN MALE RIGHT ANGLE TO N MALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8273				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			25
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.99	$66.99	$71.99	$75.99	$80.99	$65.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8327				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			26
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$62.99	$64.99	$67.99	$69.99	$61.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6198				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	27
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.99	$78.99	$85.99	$92.99	$99.99	$76.99	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C8487				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			28
7"	18CM	-	-	-	-	Custom Len.	
$59.99	$62.99	$65.99	$68.99	$71.99	$61.99	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C8504				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			29
7"	18CM	-	-	-	-	Custom Len.	
$58.99	$60.99	$63.99	$65.99	$68.99	$60.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

***Coax Performance at 1 GHz** **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

7/16 DIN MALE RIGHT ANGLE TO N MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8274				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	30
1 piece price shown. See web or call for volume pricing.				0.16" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.99	$68.99	$73.99	$77.99	$82.99	$67.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8328				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	31
1 piece price shown. See web or call for volume pricing.				0.16" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.99	$64.99	$66.99	$69.99	$71.99	$63.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6199				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	32
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.99	$81.99	$88.99	$95.99	$103.99	$79.99	See Web	

7/16 DIN MALE RIGHT ANGLE TO N FEMALE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8271				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	33
1 piece price shown. See web or call for volume pricing.				0.16" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$65.99	$69.99	$74.99	$78.99	$63.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8325				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	34
1 piece price shown. See web or call for volume pricing.				0.16" dia.			
12"	24"	36"	48"	50CM	100CM	Custom Len.	
$59.99	$61.99	$63.99	$65.99	$60.99	$64.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6196				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	35
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.99	$78.99	$85.99	$92.99	$99.99	$76.99	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C8488				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	36
1 piece price shown. See web or call for volume pricing.				0.303" dia.			
7"	18CM	-	-	-	-	Custom Len.	
$59.99	$62.99	$65.99	$68.99	$71.99	$61.99	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C8505				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	37
1 piece price shown. See web or call for volume pricing.				0.303" dia.			
7"	18CM	-	-	-	-	Custom Len.	
$58.99	$60.99	$63.99	$65.99	$68.99	$60.99	See Web	

7/16 DIN MALE RIGHT ANGLE TO N FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8272				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	38
1 piece price shown. See web or call for volume pricing.				0.16" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.99	$66.99	$71.99	$75.99	$80.99	$65.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8326				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	39
1 piece price shown. See web or call for volume pricing.				0.16" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$62.99	$64.99	$67.99	$69.99	$61.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6197				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	40
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.99	$78.99	$85.99	$92.99	$99.99	$76.99	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C8489				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	41
1 piece price shown. See web or call for volume pricing.				0.303" dia.			
7"	18CM	-	-	-	-	Custom Len.	
$59.99	$62.99	$65.99	$68.99	$71.99	$61.99	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C8506				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	42
1 piece price shown. See web or call for volume pricing.				0.303" dia.			
7"	18CM	-	-	-	-	Custom Len.	
$58.99	$60.99	$63.99	$65.99	$68.99	$60.99	See Web	

7/16 DIN MALE RIGHT ANGLE TO NEX10 MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6252				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	43
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$81.99	$88.99	$95.99	$101.99	$109.99	$85.99	See Web	

7/16 DIN FEMALE TO 7/16 DIN FEMALE



Low PIM Flexible Cable Assemblies

SPO-375 Coax, 50 Ohm

Part No. PE3C6504				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	44
1 piece price shown. See web or call for volume pricing.				0.43" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.99	$78.99	$82.99	$85.99	$89.99	$77.99	See Web	

Low PIM Corrugated Cable Assemblies

SPF-375 Coax, 50 Ohm

Part No. PE3C6510				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	45
1 piece price shown. See web or call for volume pricing.				0.435" dia.			
24"	36"	48"	60"	50CM	100CM	Custom Len.	
$80.99	$84.99	$89.99	$94.99	$78.99	$86.99	See Web	

7/16 DIN FEMALE TO N MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6224				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	46
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.99	$73.99	$79.99	$86.99	$93.99	$70.99	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C8490				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	47
1 piece price shown. See web or call for volume pricing.				0.303" dia.			
7"	18CM	-	-	-	-	Custom Len.	
$53.99	$56.99	$59.99	$62.99	$65.99	$55.99	See Web	

SPF-375 Coax, 50 Ohm

Part No. PE3C8498				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	48
1 piece price shown. See web or call for volume pricing.				0.435" dia.			
7"	18CM	-	-	-	-	Custom Len.	
$45.99	$49.99	$53.99	$57.99	$61.99	$48.59	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C8507				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	49
1 piece price shown. See web or call for volume pricing.				0.303" dia.			
7"	18CM	-	-	-	-	Custom Len.	
$52.99	$54.99	$57.99	$59.99	$61.99	$54.99	See Web	

SPO-375 Coax, 50 Ohm

Part No. PE3C8514				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	50
1 piece price shown. See web or call for volume pricing.				0.43" dia.			
7"	18CM	-	-	-	-	Custom Len.	
$44.99	$47.99	$50.99	$53.99	$56.99	$46.99	See Web	

7/16 DIN FEMALE TO N MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C8266				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	51
1 piece price shown. See web or call for volume pricing.				0.16" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$62.99	$67.99	$71.99	$76.99	$61.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8320				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	52
1 piece price shown. See web or call for volume pricing.				0.16" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$56.99	$59.99	$60.99	$63.99	$65.99	$58.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6244				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	53
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.99	$76.99	$82.99	$89.99	$96.99	$73.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

7/16 DIN FEMALE TO N FEMALE



Low PIM Corrugated Cable Assemblies

SPP-375-LLPL Coax, 50 Ohm

Part No. PE3C8517				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.402" dia.			54
7"	18CM	-	-	-	-	Custom Len.	
$50.99	$58.99	$66.99	$75.99	$83.99	$55.99	See Web	

SPO-375 Coax, 50 Ohm

Part No. PE3C8515				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			55
7"	18CM	-	-	-	-	Custom Len.	
$44.99	$47.99	$50.99	$53.99	$56.99	$46.99	See Web	

SPF-375 Coax, 50 Ohm

Part No. PE3C8499				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.435" dia.			56
7"	18CM	-	-	-	-	Custom Len.	
$45.99	$49.99	$53.99	$57.99	$61.99	$48.59	See Web	

7/16 DIN FEMALE TO NEX10 MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6260				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	57
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.99	$82.99	$89.99	$96.99	$103.99	$80.99	See Web	

10-32 MALE TO 10-32 MALE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36520				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	58
12"	24"	36"	48"	60"	72"	Custom Len.	
$83.99	$84.99	$81.99	$85.99	$86.99	$87.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36522				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	59
12"	24"	36"	48"	60"	72"	Custom Len.	
$111.99	$111.99	$119.99	$113.99	$121.99	$117.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE36524				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	60
12"	24"	36"	48"	60"	72"	Custom Len.	
$84.99	$88.99	$91.99	$101.99	$105.99	$109.99	See Web	

10-32 MALE TO 10-32 MALE RIGHT ANGLE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36526				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	61
12"	24"	36"	48"	60"	72"	Custom Len.	
$89.99	$84.99	$85.99	$85.99	$86.99	$86.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36528				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	62
12"	24"	36"	48"	60"	72"	Custom Len.	
$107.99	$109.99	$109.99	$111.99	$113.99	$113.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE36530				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	63
12"	24"	36"	48"	60"	72"	Custom Len.	
$84.99	$88.99	$92.99	$95.99	$99.99	$103.99	See Web	

10-32 MALE TO BNC MALE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C3275				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	64
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.99	$64.99	$64.99	$65.99	$66.99	$67.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36540				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	65
12"	24"	36"	48"	60"	72"	Custom Len.	
$101.99	$103.99	$105.99	$99.99	$101.99	$101.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C3424				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	66
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.99	$64.99	$67.99	$71.99	$76.99	$80.99	See Web	

10-32 MALE RIGHT ANGLE TO 10-32 MALE RIGHT ANGLE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36532				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	67
12"	24"	36"	48"	60"	72"	Custom Len.	
$82.99	$83.99	$83.99	$84.99	$84.99	$85.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36534				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	68
12"	24"	36"	48"	60"	72"	Custom Len.	
$117.99	$119.99	$119.99	$121.99	$121.99	$129.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE36536				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	69
12"	24"	36"	48"	60"	72"	Custom Len.	
$85.99	$88.99	$92.99	$96.99	$101.99	$111.99	See Web	

10-32 MALE RIGHT ANGLE TO SMP FEMALE



Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C7720				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	70
12"	24"	36"	48"	60"	50CM	Custom Len.	
$88.99	$89.99	$91.99	$92.99	$93.99	$87.99	See Web	

10-32 FEMALE TO BNC MALE



Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3W03496				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	71
12"	24"	36"	48"	60"	50CM	Custom Len.	
$83.99	$84.99	$85.99	$87.99	$88.99	$84.99	See Web	

BMA PLUG BULKHEAD TO BMA PLUG BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4899				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	72
6"	12"	24"	36"	60"	-	Custom Len.	
$87.99	$91.99	$101.99	$109.99	$127.99	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4844				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	73
6"	12"	24"	36"	60"	-	Custom Len.	
$88.99	$93.99	$103.99	$111.99	$129.99	-	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4936				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	74
6"	12"	24"	36"	60"	-	Custom Len.	
$135.99	$137.99	$139.99	$143.99	$149.99	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4950				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	75
6"	12"	24"	36"	60"	-	Custom Len.	
$105.99	$109.99	$117.99	$123.99	$141.99	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4921				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		76
6"	12"	24"	36"	60"	-	Custom Len.	
$129.99	$131.99	$131.99	$131.99	$133.99	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4872				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	77
6"	12"	24"	36"	60"	-	Custom Len.	
$89.99	$93.99	$103.99	$78.99	$125.99	-	See Web	

BMA PLUG BULKHEAD TO BMA JACK



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4904				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	78
6"	12"	24"	36"	60"	-	Custom Len.	
$153.99	$157.99	$167.99	$175.99	$193.99	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4852				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	79
6"	12"	24"	36"	60"	-	Custom Len.	
$139.99	$145.99	$153.99	$163.99	$181.99	-	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4940				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	80
6"	12"	24"	36"	60"	-	Custom Len.	
$171.99	$173.99	$177.99	$179.99	$187.99	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4953				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	81
6"	12"	24"	36"	60"	-	Custom Len.	
$187.99	$191.99	$199.99	$207.99	$223.99	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4925				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		82
6"	12"	24"	36"	60"	-	Custom Len.	
$167.99	$167.99	$169.99	$169.99	$171.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4879				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	83
6"	12"	24"	36"	60"	-	Custom Len.	
$141.99	$145.99	$155.99	$163.99	$179.99	-	See Web	

BMA PLUG BULKHEAD TO BMA JACK BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4851				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	84
6"	12"	24"	36"	60"	-	Custom Len.	
$111.99	$117.99	$123.99	$133.99	$151.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4878				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	85
6"	12"	24"	36"	60"	-	Custom Len.	
$113.99	$117.99	$125.99	$133.99	$149.99	-	See Web	

BMA PLUG BULKHEAD TO BMA JACK 2 HOLE FLANGE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4903				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	86
6"	12"	24"	36"	60"	-	Custom Len.	
$105.99	$109.99	$119.99	$125.99	$143.99	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4850				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	87
6"	12"	24"	36"	60"	-	Custom Len.	
$119.99	$121.99	$131.99	$139.99	$159.99	-	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4939				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	88
6"	12"	24"	36"	60"	-	Custom Len.	
$129.99	$131.99	$135.99	$137.99	$145.99	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4924				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		89
6"	12"	24"	36"	60"	-	Custom Len.	
$125.99	$125.99	$125.99	$127.99	$129.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4877				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	90
6"	12"	24"	36"	60"	-	Custom Len.	
$121.99	$123.99	$131.99	$139.99	$155.99	-	See Web	

BMA PLUG BULKHEAD TO BMA JACK RIGHT ANGLE 2 HOLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4905				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	91
6"	12"	24"	36"	60"	-	Custom Len.	
$139.99	$143.99	$151.99	$161.99	$179.99	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4853				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	92
6"	12"	24"	36"	60"	-	Custom Len.	
$131.99	$137.99	$145.99	$155.99	$173.99	-	See Web	

Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE3C4954				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	93
6"	12"	24"	36"	60"	-	Custom Len.	
$129.99	$135.99	$143.99	$151.99	$167.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4880				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	94
6"	12"	24"	36"	60"	-	Custom Len.	
$133.99	$137.99	$145.99	$155.99	$171.99	-	See Web	

BMA PLUG BULKHEAD TO BNC MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4918				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	95
6"	12"	24"	36"	60"	-	Custom Len.	
$86.99	$90.99	$99.99	$109.99	$125.99	-	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4949				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	96
6"	12"	24"	36"	60"	-	Custom Len.	
$86.99	$88.99	$91.99	$95.99	$103.99	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4963				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	97
6"	12"	24"	36"	60"	-	Custom Len.	
$72.99	$76.99	$84.99	$92.99	$109.99	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4935				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		98
6"	12"	24"	36"	60"	-	Custom Len.	
$80.99	$81.99	$82.99	$82.99	$84.99	-	See Web	

BMA PLUG BULKHEAD TO N MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4912				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	99
6"	12"	24"	36"	60"	-	Custom Len.	
$77.99	$81.99	$90.99	$99.99	$117.99	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4860				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	1
6"	12"	24"	36"	60"	-	Custom Len.	
$77.99	$82.99	$91.99	$101.99	$119.99	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4945				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	2
6"	12"	24"	36"	60"	-	Custom Len.	
$113.99	$99.99	$99.99	$103.99	$107.99	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4959				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	3
6"	12"	24"	36"	60"	-	Custom Len.	
$84.99	$88.99	$96.99	$105.99	$121.99	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4931				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		4
6"	12"	24"	36"	60"	-	Custom Len.	
$92.99	$92.99	$93.99	$94.99	$96.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4887				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	5
6"	12"	24"	36"	60"	-	Custom Len.	
$78.99	$82.99	$90.99	$99.99	$115.99	-	See Web	

BMA PLUG BULKHEAD TO SMA MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4906				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	6
6"	12"	24"	36"	60"	-	Custom Len.	
$67.99	$72.99	$81.99	$90.99	$109.99	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4854				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	7
6"	12"	24"	36"	60"	-	Custom Len.	
$69.99	$73.99	$82.99	$92.99	$111.99	-	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4942				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	8
6"	12"	24"	36"	60"	-	Custom Len.	
$90.99	$92.99	$95.99	$99.99	$107.99	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4955				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	9
6"	12"	24"	36"	60"	-	Custom Len.	
$77.99	$81.99	$90.99	$98.99	$115.99	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4927				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		10
6"	12"	24"	36"	60"	-	Custom Len.	
$84.99	$85.99	$86.99	$87.99	$89.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4881				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	11
6"	12"	24"	36"	60"	-	Custom Len.	
$69.99	$74.99	$82.99	$90.99	$107.99	-	See Web	

BMA PLUG BULKHEAD TO SMA MALE RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4909				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	12
6"	12"	24"	36"	60"	-	Custom Len.	
$70.99	$75.99	$84.99	$93.99	$111.99	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4857				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	13
6"	12"	24"	36"	60"	-	Custom Len.	
$71.99	$75.99	$85.99	$94.99	$113.99	-	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4386				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	14
6"	12"	24"	36"	60"	-	Custom Len.	
$109.99	$111.99	$115.99	$117.99	$123.99	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4957				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	15
6"	12"	24"	36"	60"	-	Custom Len.	
$89.99	$94.99	$103.99	$111.99	$125.99	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4929				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		16
6"	12"	24"	36"	60"	-	Custom Len.	
$97.99	$99.99	$101.99	$99.99	$101.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4884				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	17
6"	12"	24"	36"	60"	-	Custom Len.	
$72.99	$76.99	$84.99	$93.99	$109.99	-	See Web	

BMA PLUG BULKHEAD TO SMP FEMALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4866				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	18
6"	12"	24"	36"	60"	-	Custom Len.	
$79.99	$84.99	$93.99	$103.99	$119.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4893				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	19
6"	12"	24"	36"	60"	-	Custom Len.	
$80.99	$84.99	$93.99	$101.99	$117.99	-	See Web	

BMA PLUG BULKHEAD TO SMP FEMALE RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4869				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	20
6"	12"	24"	36"	60"	-	Custom Len.	
$93.99	$98.99	$107.99	$117.99	$133.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4896				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	21
6"	12"	24"	36"	60"	-	Custom Len.	
$95.99	$99.99	$107.99	$117.99	$131.99	-	See Web	

BMA PLUG BULKHEAD TO TNC MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4915				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	22
6"	12"	24"	36"	60"	-	Custom Len.	
$73.99	$77.99	$86.99	$95.99	$113.99	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4863				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	23
6"	12"	24"	36"	60"	-	Custom Len.	
$73.99	$78.99	$87.99	$96.99	$115.99	-	See Web	

Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE3C4961				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	24
6"	12"	24"	36"	60"	-	Custom Len.	
$77.99	$81.99	$90.99	$98.99	$115.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4890				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	25
6"	12"	24"	36"	60"	-	Custom Len.	
$74.99	$78.99	$87.99	$95.99	$111.99	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

BMA JACK TO BMA JACK



Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4901				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	26
6"	12"	24"	36"	60"	-	Custom Len.	
$221.99	$225.99	$233.99	$243.99	$261.99	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4848				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	27
6"	12"	24"	36"	60"	-	Custom Len.	
$191.99	$197.99	$205.99	$215.99	$233.99	-	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4938				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	28
6"	12"	24"	36"	60"	-	Custom Len.	
$207.99	$209.99	$213.99	$217.99	$223.99	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4951				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	29
6"	12"	24"	36"	60"	-	Custom Len.	
$269.99	$273.99	$283.99	$291.99	$307.99	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4923				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		30
6"	12"	24"	36"	60"	-	Custom Len.	
$205.99	$205.99	$205.99	$207.99	$209.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4875				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	31
6"	12"	24"	36"	60"	-	Custom Len.	
$195.99	$199.99	$207.99	$215.99	$231.99	-	See Web	

BMA JACK TO BNC MALE



Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4920				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	32
6"	12"	24"	36"	60"	-	Custom Len.	
$153.99	$157.99	$165.99	$175.99	$193.99	-	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4948				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	33
6"	12"	24"	36"	60"	-	Custom Len.	
$121.99	$123.99	$127.99	$131.99	$137.99	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4964				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	34
6"	12"	24"	36"	60"	-	Custom Len.	
$155.99	$159.99	$167.99	$175.99	$191.99	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4934				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		35
6"	12"	24"	36"	60"	-	Custom Len.	
$119.99	$119.99	$121.99	$121.99	$123.99	-	See Web	

BMA JACK TO N MALE



Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4914				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	36
6"	12"	24"	36"	60"	-	Custom Len.	
$143.99	$147.99	$157.99	$165.99	$183.99	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4862				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	37
6"	12"	24"	36"	60"	-	Custom Len.	
$129.99	$133.99	$143.99	$151.99	$169.99	-	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4944				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	38
6"	12"	24"	36"	60"	-	Custom Len.	
$133.99	$135.99	$139.99	$143.99	$149.99	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4960				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	39
6"	12"	24"	36"	60"	-	Custom Len.	
$167.99	$171.99	$179.99	$187.99	$203.99	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4930				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		40
6"	12"	24"	36"	60"	-	Custom Len.	
$129.99	$129.99	$131.99	$131.99	$133.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4889				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	41
6"	12"	24"	36"	60"	-	Custom Len.	
$131.99	$135.99	$143.99	$151.99	$167.99	-	See Web	

BMA JACK TO SMA MALE



Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4908				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	42
6"	12"	24"	36"	60"	-	Custom Len.	
$133.99	$139.99	$147.99	$157.99	$175.99	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4856				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	43
6"	12"	24"	36"	60"	-	Custom Len.	
$121.99	$125.99	$133.99	$153.99	$161.99	-	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4941				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	44
6"	12"	24"	36"	60"	-	Custom Len.	
$127.99	$127.99	$131.99	$135.99	$141.99	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4956				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	45
6"	12"	24"	36"	60"	-	Custom Len.	
$159.99	$165.99	$173.99	$181.99	$197.99	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4926				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		46
6"	12"	24"	36"	60"	-	Custom Len.	
$123.99	$123.99	$125.99	$123.99	$125.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4883				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	47
6"	12"	24"	36"	60"	-	Custom Len.	
$123.99	$127.99	$135.99	$143.99	$159.99	-	See Web	

BMA JACK TO SMA MALE RIGHT ANGLE



Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4911				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	48
6"	12"	24"	36"	60"	-	Custom Len.	
$137.99	$141.99	$151.99	$159.99	$177.99	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4859				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	49
6"	12"	24"	36"	60"	-	Custom Len.	
$123.99	$127.99	$137.99	$145.99	$163.99	-	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4943				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	50
6"	12"	24"	36"	60"	-	Custom Len.	
$145.99	$145.99	$149.99	$153.99	$159.99	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

RG400/U Coax, 50 Ohm

Part No. PE3C4958				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	51
6"	12"	24"	36"	60"	-	Custom Len.	
$171.99	$177.99	$185.99	$193.99	$209.99	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4928				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		52
6"	12"	24"	36"	60"	-	Custom Len.	
$133.99	$135.99	$135.99	$135.99	$137.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4886				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	53
6"	12"	24"	36"	60"	-	Custom Len.	
$125.99	$129.99	$137.99	$145.99	$161.99	-	See Web	

BMA JACK TO SMP FEMALE



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4868				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	54
6"	12"	24"	36"	60"	-	Custom Len.	
$131.99	$135.99	$145.99	$153.99	$171.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4895				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	55
6"	12"	24"	36"	60"	-	Custom Len.	
$133.99	$137.99	$145.99	$153.99	$169.99	-	See Web	

BMA JACK TO SMP FEMALE RIGHT ANGLE



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4871				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	56
6"	12"	24"	36"	60"	-	Custom Len.	
$145.99	$149.99	$159.99	$167.99	$185.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4898				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	57
6"	12"	24"	36"	60"	-	Custom Len.	
$147.99	$151.99	$159.99	$167.99	$185.99	-	See Web	

BMA JACK TO TNC MALE



Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4917				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	58
6"	12"	24"	36"	60"	-	Custom Len.	
$139.99	$143.99	$153.99	$161.99	$179.99	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4865				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	59
6"	12"	24"	36"	60"	-	Custom Len.	
$125.99	$129.99	$139.99	$147.99	$165.99	-	See Web	

Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE3C4962				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	60
6"	12"	24"	36"	60"	-	Custom Len.	
$161.99	$165.99	$173.99	$181.99	$197.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4892				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	61
6"	12"	24"	36"	60"	-	Custom Len.	
$127.99	$131.99	$139.99	$147.99	$163.99	-	See Web	

BMA JACK BULKHEAD TO BMA JACK BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4846				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	62
6"	12"	24"	36"	60"	-	Custom Len.	
$133.99	$137.99	$147.99	$155.99	$175.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4874				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	63
6"	12"	24"	36"	60"	-	Custom Len.	
$135.99	$139.99	$147.99	$155.99	$173.99	-	See Web	

BMA JACK 2 HOLE FLANGE TO BMA JACK 2 HOLE FLANGE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4900				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	64
6"	12"	24"	36"	60"	-	Custom Len.	
$121.99	$125.99	$133.99	$143.99	$161.99	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4845				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	65
6"	12"	24"	36"	60"	-	Custom Len.	
$147.99	$151.99	$161.99	$169.99	$187.99	-	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4937				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	66
6"	12"	24"	36"	60"	-	Custom Len.	
$123.99	$125.99	$129.99	$133.99	$139.99	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4922				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		67
6"	12"	24"	36"	60"	-	Custom Len.	
$121.99	$121.99	$121.99	$123.99	$125.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4873				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	68
6"	12"	24"	36"	60"	-	Custom Len.	
$149.99	$153.99	$161.99	$169.99	$187.99	-	See Web	

BMA JACK 2 HOLE FLANGE TO BNC MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4919				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	69
6"	12"	24"	36"	60"	-	Custom Len.	
$103.99	$109.99	$117.99	$125.99	$143.99	-	See Web	

BMA JACK 2 HOLE FLANGE TO N MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4913				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	70
6"	12"	24"	36"	60"	-	Custom Len.	
$94.99	$98.99	$109.99	$117.99	$133.99	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4861				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	71
6"	12"	24"	36"	60"	-	Custom Len.	
$107.99	$113.99	$119.99	$129.99	$147.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4888				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	72
6"	12"	24"	36"	60"	-	Custom Len.	
$109.99	$113.99	$121.99	$129.99	$145.99	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

BMA JACK 2 HOLE FLANGE TO SMA MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4907				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W
6"	12"	24"	36"	60"	-	Custom Len.
$84.99	$89.99	$98.99	$107.99	$123.99	-	See Web

73

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4855				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	24"	36"	60"	-	Custom Len.
$99.99	$103.99	$113.99	$121.99	$139.99	-	See Web

74

Standard Semi-Rigid Cable Assemblies

RG402/U Coax, 50 Ohm

Part No. PE3W06981				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					11.1 dB/100ft	450 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$115.99	$121.99	$131.99	$141.99	$151.99	$121.99	See Web

75

RG405/U Coax, 50 Ohm

Part No. PE3C4882				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W
6"	12"	24"	36"	60"	-	Custom Len.
$101.99	$105.99	$113.99	$121.99	$137.99	-	See Web

76

RG402/U Coax, 50 Ohm

Part No. PE3W08629				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					11.1 dB/100ft	450 W
24"	100CM	-	-	-	-	Custom Len.
$121.99	$131.99	-	-	-	-	See Web

77

BMA JACK 2 HOLE FLANGE TO SMA MALE RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4910				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W
6"	12"	24"	36"	60"	-	Custom Len.
$88.99	$92.99	$101.99	$111.99	$127.99	-	See Web

78

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4858				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	24"	36"	60"	-	Custom Len.
$101.99	$107.99	$115.99	$123.99	$141.99	-	See Web

79

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4885				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W
6"	12"	24"	36"	60"	-	Custom Len.
$103.99	$107.99	$115.99	$123.99	$139.99	-	See Web

80

BMA JACK 2 HOLE FLANGE TO SMP FEMALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4867				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	24"	36"	60"	-	Custom Len.
$109.99	$115.99	$121.99	$131.99	$149.99	-	See Web

81

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4894				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W
6"	12"	24"	36"	60"	-	Custom Len.
$111.99	$115.99	$123.99	$131.99	$147.99	-	See Web

82

BMA JACK 2 HOLE FLANGE TO SMP FEMALE RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4870				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	24"	36"	60"	-	Custom Len.
$123.99	$127.99	$137.99	$145.99	$163.99	-	See Web

83

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4897				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W
6"	12"	24"	36"	60"	-	Custom Len.
$125.99	$129.99	$137.99	$145.99	$161.99	-	See Web

84

BMA JACK 2 HOLE FLANGE TO TNC MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4916				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W
6"	12"	24"	36"	60"	-	Custom Len.
$90.99	$95.99	$105.99	$113.99	$129.99	-	See Web

85

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4864				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	24"	36"	60"	-	Custom Len.
$103.99	$109.99	$117.99	$125.99	$143.99	-	See Web

86

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4891				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W
6"	12"	24"	36"	60"	-	Custom Len.
$105.99	$109.99	$117.99	$125.99	$141.99	-	See Web

87

BMA JACK RIGHT ANGLE 2 HOLE FLANGE TO



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4902				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W
6"	12"	24"	36"	60"	-	Custom Len.
$191.99	$195.99	$165.99	$213.99	$231.99	-	See Web

88

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4849				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	24"	36"	60"	-	Custom Len.
$175.99	$181.99	$189.99	$199.99	$217.99	-	See Web

89

Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE3C4952				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W
6"	12"	24"	36"	60"	-	Custom Len.
$157.99	$161.99	$169.99	$177.99	$193.99	-	See Web

90

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4876				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W
6"	12"	24"	36"	60"	-	Custom Len.
$179.99	$183.99	$191.99	$199.99	$215.99	-	See Web

91

BNC MALE TO 7/16 DIN FEMALE



Standard Flexible Cable Assemblies

LMR-400-UF Coax, 50 Ohm

Part No. PE3W10097				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	5 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$151.99	$153.99	$155.99	$157.99	$159.99	$149.99	See Web

92

BNC MALE TO NMO MOUNT SEXLESS



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37844				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
60"	120"	180"	-	-	-	Custom Len.
$52.99	$61.99	$61.99	-	-	-	See Web

93

See Our Website For Current Pricing & Real-Time Stock Availability!

BNC MALE TO BNC MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE36066				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	94
12"	24"	36"	48"	60"	-	Custom Len.	
$36.59	$37.59	$38.59	$39.79	$40.79	-	See Web	

PE-C200 Coax, 50 Ohm

Part No. PE35256				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10.8 dB/100ft	170 W	95
12"	24"	36"	48"	60"	-	Custom Len.	
$58.99	$61.99	$63.99	$71.99	$77.99	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE36219				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	96
12"	24"	36"	48"	60"	-	Custom Len.	
$68.99	$76.99	$78.99	$74.99	$81.99	-	See Web	

PE-C300 Coax, 50 Ohm

Part No. PE35729				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	6.3 dB/100ft	350 W	97
12"	24"	36"	48"	60"	-	Custom Len.	
$66.99	$70.99	$73.99	$77.99	$87.99	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE35874				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	98
12"	24"	36"	48"	60"	-	Custom Len.	
$107.99	$109.99	$113.99	$119.99	$125.99	-	See Web	

LMR-200-UF Coax, 50 Ohm

Part No. PE3C2220				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.							99
12"	24"	36"	48"	60"	50CM	Custom Len.	
$57.99	$60.99	$62.99	$65.99	$68.99	$59.99	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3W01041				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.			1
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.99	$67.99	$68.99	$69.99	$70.99	$66.99	See Web	

LMR-400-DB Coax, 50 Ohm

Part No. PE3W01357				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.15 dB/100ft		2
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.99	$75.99	$76.99	$78.99	$80.99	$74.99	See Web	

PE-SF200LL Coax, 50 Ohm

Part No. PE3TC1100				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.185" dia.			3
24"	36"	48"	72"	100CM	200CM	Custom Len.	
$88.99	$103.99	$117.99	$145.99	$107.99	$153.99	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34173					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.047" dia.	36 dB/100ft	32 W	4
6"	12"	18"	24"	36"	48"	Custom Len.		
$107.99	$111.99	$115.99	$119.99	$127.99	$135.99	See Web		

PE-SR401FL Coax, 50 Ohm

Part No. PE34166					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						7.6 dB/100ft	1,400 W	5
6"	12"	18"	24"	36"	48"	Custom Len.		
$155.99	$165.99	$173.99	$183.99	$201.99	$219.99	See Web		

PE-SR402FL Coax, 50 Ohm

Part No. PE3462					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						11.88 dB/100ft	450 W	6
6"	12"	18"	24"	36"	48"	Custom Len.		
$107.99	$111.99	$115.99	$119.99	$119.99	$139.99	See Web		

PE-SR405FL Coax, 50 Ohm

Part No. PE3776					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22.5 dB/100ft	130 W	7
6"	12"	18"	24"	36"	48"	Custom Len.		
$105.99	$113.99	$111.99	$117.99	$139.99	$141.99	See Web		

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3807				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	8
12"	24"	36"	48"	60"	72"	Custom Len.	
$96.99	$101.99	$111.99	$107.99	$111.99	$123.99	See Web	

RG8X Coax, 50 Ohm

Part No. PE3264				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13.5 dB/100ft	60 W	9
12"	24"	36"	48"	60"	-	Custom Len.	
$82.99	$93.99	$97.99	$93.99	$107.99	-	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3067				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	10
12"	18"	24"	30"	36"	48"	Custom Len.	
$38.99	$39.39	$39.99	$41.99	$40.79	$41.79	See Web	

RG58-P Coax, 50 Ohm

Part No. PE3999				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.159" dia.	17.3 dB/100ft	632 W	11
12"	24"	36"	48"	60"	-	Custom Len.	
$59.99	$65.99	$80.99	$77.99	$83.99	-	See Web	

RG141A/U Coax, 50 Ohm

Part No. PE35148				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W	12
12"	24"	36"	48"	60"	-	Custom Len.	
$58.99	$66.99	$75.99	$84.99	$93.99	-	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3495				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.		650 W	13
12"	24"	36"	48"	60"	72"	Custom Len.	
$39.39	$46.99	$54.99	$61.99	$69.99	$77.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C2295				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	14
12"	24"	36"	48"	60"	72"	Custom Len.	
$38.59	$39.39	$39.99	$40.79	$41.59	$42.39	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE33130				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	15
12"	24"	36"	48"	60"	-	Custom Len.	
$80.99	$81.99	$83.99	$84.99	$85.99	-	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3C2034				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	16
12"	24"	36"	48"	60"	72"	Custom Len.	
$45.39	$48.39	$51.99	$54.99	$58.99	$61.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3749				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	17
12"	24"	36"	48"	60"	72"	Custom Len.	
$95.99	$97.99	$103.99	$101.99	$103.99	$105.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3906				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	18
12"	24"	36"	48"	60"	72"	Custom Len.	
$94.99	$111.99	$119.99	$129.99	$129.99	$137.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3087				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	19
6"	8"	10"	12"	24"	36"	Custom Len.	
Call	Call	Call	$37.59	$41.19	$44.79	See Web	

RG303/U Coax, 50 Ohm

Part No. PE3W00393				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.17" dia.	14 dB/100ft	650 W	20
12"	24"	36"	48"	60"	50CM	Custom Len.	
$43.99	$52.99	$61.99	$69.99	$77.99	$49.59	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C2416				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	21
12"	24"	36"	48"	60"	72"	Custom Len.	
$43.39	$47.39	$51.99	$55.99	$59.99	$62.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3582				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	22
12"	24"	36"	48"	60"	72"	Custom Len.	
$52.99	$61.99	$70.99	$79.99	$89.99	$98.99	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE34035				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	23
12"	24"	36"	48"	60"	-	Custom Len.	
$31.59	$42.99	$54.99	$67.99	$79.99	-	See Web	

LMR-195 Coax, 50 Ohm

Part No. PE3C0054				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		24
12"	24"	36"	48"	60"	-	Custom Len.	
$31.39	$31.59	$32.39	$33.39	$34.39	-	See Web	

LMR-240-UF Coax, 50 Ohm

Part No. PE3W08340				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft		25
12"	36"	150CM	200CM	-	-	Custom Len.	
$68.99	$68.99	$71.99	$74.99	-	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

For our complete selection of cable assemblies, please visit our website

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE34177				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W
6"	12"	18"	24"	36"	48"	Custom Len.
$119.99	$119.99	$125.99	$131.99	$145.99	$157.99	See Web

26

PE-SR047AL Coax, 50 Ohm

Part No. PE34168				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W
6"	12"	18"	24"	36"	48"	Custom Len.
$107.99	$113.99	$119.99	$123.99	$133.99	$143.99	See Web

27

PE-SR402AL Coax, 50 Ohm

Part No. PE34164				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W
6"	12"	18"	24"	36"	48"	Custom Len.
$91.99	$103.99	$103.99	$109.99	$119.99	$129.99	See Web

28

PE-SR405AL Coax, 50 Ohm

Part No. PE34162				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W
6"	12"	18"	24"	36"	48"	Custom Len.
$91.99	$96.99	$101.99	$107.99	$117.99	$125.99	See Web

29

RG401/U Coax, 50 Ohm

Part No. PE34170				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W
6"	12"	18"	24"	36"	48"	Custom Len.
$163.99	$175.99	$189.99	$201.99	$229.99	$279.99	See Web

30

RG402/U Coax, 50 Ohm

Part No. PE3445				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W
6"	12"	18"	24"	36"	48"	Custom Len.
$103.99	$109.99	$107.99	$111.99	$127.99	$127.99	See Web

31

RG405/U Coax, 50 Ohm

Part No. PE3678				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W
6"	12"	18"	24"	36"	48"	Custom Len.
$91.99	$96.99	$107.99	$105.99	$113.99	$121.99	See Web

32

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34175				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W
6"	12"	18"	24"	36"	48"	Custom Len.
$157.99	$167.99	$179.99	$189.99	$211.99	$231.99	See Web

33

Standard Flexible Cable Assemblies

RG55B/U Coax, 53 Ohm

Part No. PE3583				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W
12"	24"	36"	48"	60"	72"	Custom Len.
$41.39	$44.59	$47.99	$51.99	$54.99	$58.99	See Web

34

RG59B/U Coax, 75 Ohm

Part No. PE3075				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	74 W
12"	18"	24"	30"	36"	48"	Custom Len.
$33.39	$34.99	$34.59	$35.19	$35.79	$36.99	See Web

35

RG62A/U Coax, 93 Ohm

Part No. PE3081				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.239" dia.	8.7 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$40.99	$46.19	$48.19	$50.99	$52.99	$54.99	See Web

36

RG179B/U Coax, 75 Ohm

Part No. PE3C3349				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	29.15 dB/100ft	240 W
12"	24"	36"	48"	60"	72"	Custom Len.
$46.59	$46.19	$49.19	$51.99	$54.99	$62.99	See Web

37

RG180B/U Coax, 95 Ohm

Part No. PE33574				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.145" dia.		250 W
12"	24"	36"	48"	60"	-	Custom Len.
$54.99	$60.99	$60.99	$70.99	$70.99	-	See Web

38

RG302/U Coax, 75 Ohm

Part No. PE33123				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.206" dia.	13 dB/100ft	650 W
12"	24"	36"	48"	60"	-	Custom Len.
$38.79	$46.19	$53.99	$60.99	$67.99	-	See Web

39

BNC MALE TO
BNC MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

PE-C240 Coax, 50 Ohm

Part No. PE38997				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W
12"	24"	36"	48"	60"	-	Custom Len.
$70.99	$67.99	$69.99	$73.99	$77.99	-	See Web

40

LMR-195 Coax, 50 Ohm

Part No. PE3W01992				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$54.99	$55.99	$56.99	$57.99	$58.99	$55.99	See Web

41

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE35580				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W
12"	24"	36"	48"	60"	-	Custom Len.
$105.99	$115.99	$123.99	$131.99	$141.99	-	See Web

42

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3327				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W
12"	24"	36"	48"	60"	72"	Custom Len.
$103.99	$107.99	$111.99	$113.99	$117.99	$121.99	See Web

43

RG58C/U Coax, 50 Ohm

Part No. PE3020				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	72"	Custom Len.
$63.99	$64.99	$65.99	$66.99	$67.99	$68.99	See Web

44

RG59B/U Coax, 75 Ohm

Part No. PE3508				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$60.99	$56.99	$62.99	$58.99	$59.99	$66.99	See Web

45

RG142B/U Coax, 50 Ohm

Part No. PE3082				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft	
12"	24"	36"	48"	60"	72"	Custom Len.
$60.99	$68.99	$75.99	$79.99	$86.99	$93.99	See Web

46

RG174A/U Coax, 50 Ohm

Part No. PE3C3404				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W
12"	24"	36"	48"	60"	72"	Custom Len.
$68.99	$69.99	$66.99	$70.99	$71.99	$68.99	See Web

47

RG179B/U Coax, 75 Ohm

Part No. PE3C3375				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	29.15 dB/100ft	240 W
12"	24"	36"	48"	60"	72"	Custom Len.
$75.99	$77.99	$88.99	$83.99	$86.99	$89.99	See Web

48

RG188A/U Coax, 50 Ohm

Part No. PE3C3377				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$81.99	$84.99	$87.99	$83.99	$86.99	$97.99	See Web

49

RG213/U Coax, 50 Ohm

Part No. PE3355				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W
12"	24"	36"	48"	60"	72"	Custom Len.
$107.99	$115.99	$111.99	$113.99	$115.99	$117.99	See Web

50

RG214/U Coax, 50 Ohm

Part No. PE3325				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W
12"	24"	36"	48"	60"	72"	Custom Len.
$111.99	$113.99	$121.99	$129.99	$139.99	$147.99	See Web

51

RG223/U Coax, 50 Ohm

Part No. PE3689				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W
12"	24"	36"	48"	60"	72"	Custom Len.
$56.99	$60.99	$63.99	$67.99	$68.99	$71.99	See Web

52

RG316/U Coax, 50 Ohm

Part No. PE3C3391				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$77.99	$76.99	$80.99	$84.99	$93.99	$97.99	See Web

53

RG400/U Coax, 50 Ohm

Part No. PE3116				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W
12"	24"	36"	48"	60"	72"	Custom Len.
$81.99	$90.99	$99.99	$109.99	$111.99	$125.99	See Web

54

Standard Semi-Rigid Cable Assemblies

RG402/U Coax, 50 Ohm

Part No. PE39108				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W
12"	24"	36"	48"	60"	-	Custom Len.
$101.99	$109.99	$117.99	$125.99	$133.99	-	See Web

55

See Our Website For Current Pricing & Real-Time Stock Availability!

For Custom Lengths, Metric Lengths or Special Configurations, Please call (949) 261-1920

BNC MALE TO BNC FEMALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38344				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	56
12"	24"	36"	48"	60"	-	Custom Len.	
$36.79	$37.59	$38.59	$39.39	$40.39	-	See Web	

PE-SF200LL Coax, 50 Ohm

Part No. PE3TC1101				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.185" dia.			57
24"	36"	48"	72"	100CM	200CM	Custom Len.	
$88.99	$103.99	$117.99	$145.99	Call	Call	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3360				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	58
12"	24"	36"	48"	60"	72"	Custom Len.	
$113.99	$117.99	$121.99	$123.99	$125.99	$137.99	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3047				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	59
12"	24"	36"	48"	60"	72"	Custom Len.	
$48.19	$49.19	$50.99	$51.99	$52.99	$53.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3777				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	60
12"	24"	36"	48"	60"	72"	Custom Len.	
$46.19	$53.99	$60.99	$66.99	$74.99	$81.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3325				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	61
12"	24"	36"	48"	60"	-	Custom Len.	
$52.99	$53.99	$51.99	$55.99	$55.99	-	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3C3453				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	62
12"	24"	36"	48"	60"	72"	Custom Len.	
$51.99	$54.99	$56.99	$59.99	$61.99	$64.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3949				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	63
12"	24"	36"	48"	60"	72"	Custom Len.	
$109.99	$111.99	$113.99	$115.99	$117.99	$117.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3371				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	64
12"	24"	36"	48"	60"	72"	Custom Len.	
$113.99	$121.99	$131.99	$139.99	$149.99	$157.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3606				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft		65
12"	24"	36"	48"	60"	72"	Custom Len.	
$43.79	$43.39	$51.99	$55.99	$54.99	$57.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C3344				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		66
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.99	$58.99	$62.99	$66.99	$66.99	$74.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3627				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	67
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.99	$65.99	$73.99	$82.99	$91.99	$109.99	See Web	

RG55B/U Coax, 53 Ohm

Part No. PE3375				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	68
12"	24"	36"	48"	60"	72"	Custom Len.	
$42.79	$45.59	$48.59	$51.99	$54.99	$57.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3792				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	69
12"	24"	36"	48"	60"	72"	Custom Len.	
$35.99	$37.19	$38.39	$42.79	$40.79	$41.99	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE3368				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	70
12"	24"	36"	48"	60"	72"	Custom Len.	
$34.59	$36.19	$37.79	$39.59	$41.19	$42.99	See Web	

BNC MALE TO BNC FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38804				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	71
12"	24"	36"	48"	60"	-	Custom Len.	
$42.59	$46.99	$44.39	$45.19	$46.19	-	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3440				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	72
12"	24"	36"	48"	60"	72"	Custom Len.	
$119.99	$121.99	$123.99	$127.99	$131.99	$133.99	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3649				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	73
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.99	$56.99	$57.99	$58.99	$59.99	$60.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3436				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	74
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.99	$63.99	$70.99	$77.99	$84.99	$91.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3397				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	75
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.99	$60.99	$61.99	$57.99	$57.99	$58.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3C3399				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	76
12"	24"	36"	48"	60"	72"	Custom Len.	
$52.99	$55.99	$58.99	$60.99	$62.99	$65.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3450				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	77
12"	24"	36"	48"	60"	72"	Custom Len.	
$115.99	$117.99	$119.99	$121.99	$121.99	$123.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3427				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	78
12"	24"	36"	48"	60"	72"	Custom Len.	
$119.99	$127.99	$135.99	$143.99	$153.99	$161.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3557				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	79
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.99	$57.99	$60.99	$69.99	$73.99	$71.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C3446				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	80
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.99	$58.99	$61.99	$64.99	$67.99	$71.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3423				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	81
12"	24"	36"	48"	60"	72"	Custom Len.	
$71.99	$80.99	$89.99	$99.99	$109.99	$109.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3103				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	82
12"	24"	36"	48"	60"	72"	Custom Len.	
$51.99	$53.99	$54.99	$55.99	$56.99	$63.99	See Web	

BNC MALE TO FAKRA PLUG



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C7715				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	83
12"	24"	36"	48"	60"	50CM	Custom Len.	
$34.79	$35.39	$36.19	$36.99	$37.59	$34.59	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

BNC MALE TO MHV MALE



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3W00032				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.		44 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$55.99	$57.99	$58.99	$59.99	$60.99	$56.99	See Web

84

BNC MALE TO N MALE



Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE3061				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft	
12"	24"	36"	48"	60"	72"	Custom Len.
$55.99	$62.99	$70.99	$78.99	$79.99	$86.99	See Web

85

Part No. PE3W06862				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$49.19	$56.99	$63.99	$70.99	$77.99	$53.99	See Web

86

LMR-240 Coax, 50 Ohm

Part No. PE3W05881				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$48.39	$49.59	$50.99	$51.99	$52.99	$49.19	See Web

87

BNC MALE TO SHV PLUG



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3W00148				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.		44 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$73.99	$74.99	$75.99	$76.99	$77.99	$74.99	See Web

88

BNC MALE TO SSMC PLUG



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4430				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
6"	12"	18"	24"	36"	48"	Custom Len.
$58.99	$59.99	$54.99	$60.99	$55.99	$62.99	See Web

89

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4450				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	18"	24"	36"	48"	Custom Len.
$86.99	$99.99	$95.99	$101.99	$109.99	$119.99	See Web

90

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4397				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
6"	12"	18"	24"	36"	48"	Custom Len.
$84.99	$93.99	$85.99	$86.99	$96.99	$97.99	See Web

91

RG316/U Coax, 50 Ohm

Part No. PE3C4413				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
6"	12"	18"	24"	36"	48"	Custom Len.
$65.99	$71.99	$68.99	$70.99	$78.99	$77.99	See Web

92

BNC MALE TO SSMC PLUG RIGHT ANGLE



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4431				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
6"	12"	18"	24"	36"	48"	Custom Len.
$54.99	$54.99	$50.99	$50.99	$51.99	$52.99	See Web

93

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4487				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	18"	24"	36"	48"	Custom Len.
$82.99	$87.99	$91.99	$96.99	$105.99	$115.99	See Web

94

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4466				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
6"	12"	18"	24"	36"	48"	Custom Len.
$74.99	$79.99	$75.99	$76.99	$77.99	$78.99	See Web

95

RG316/U Coax, 50 Ohm

Part No. PE3C4414				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
6"	12"	18"	24"	36"	48"	Custom Len.
$61.99	$69.99	$64.99	$66.99	$69.99	$73.99	See Web

96

RG316-DS Coax, 50 Ohm

Part No. PE3C4476				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W
6"	12"	18"	24"	36"	48"	Custom Len.
$66.99	$68.99	$63.99	$65.99	$69.99	$80.99	See Web

97

BNC MALE TO SSMC JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4488				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	18"	24"	36"	48"	Custom Len.
$77.99	$82.99	$87.99	$91.99	$101.99	$111.99	See Web

98

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4398				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
6"	12"	18"	24"	36"	48"	Custom Len.
$79.99	$80.99	$81.99	$81.99	$82.99	$83.99	See Web

99

BNC MALE TO STRAIGHT CUT LEAD SEXLESS



Standard Flexible Cable Assemblies

RG188A/U Coax, 50 Ohm

Part No. PE3C3583				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W
12"	50CM	24"	36"	100CM	48"	Custom Len.
$29.99	$31.19	$32.39	$35.39	$36.19	$38.39	See Web

1

BNC MALE TO UHF FEMALE



Standard Flexible Cable Assemblies

RG55B/U Coax, 53 Ohm

Part No. PE3C8015				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$44.39	$47.99	$51.99	$55.99	$58.99	$42.99	See Web

2

BNC MALE RIGHT ANGLE TO BNC MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE39185				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
$71.99	$72.99	$73.99	$74.99	$75.99	-	See Web

3

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3378				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W
12"	24"	36"	48"	60"	72"	Custom Len.
$123.99	$125.99	$129.99	$131.99	$135.99	$139.99	See Web

4

RG58C/U Coax, 50 Ohm

Part No. PE3025				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	72"	Custom Len.
$86.99	$87.99	$88.99	$89.99	$90.99	$91.99	See Web

5

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

RG142B/U Coax, 50 Ohm

Part No. PE3044				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		6
12"	24"	36"	48"	60"	72"	Custom Len.	
$88.99	$96.99	$98.99	$105.99	$113.99	$119.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3373				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	7
12"	24"	36"	48"	60"	72"	Custom Len.	
$105.99	$97.99	$98.99	$98.99	$99.99	$99.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3351				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	8
12"	24"	36"	48"	60"	72"	Custom Len.	
$98.99	$101.99	$105.99	$107.99	$109.99	$123.99	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE3381				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	9
12"	24"	36"	48"	60"	72"	Custom Len.	
$92.99	$96.99	$101.99	$105.99	$109.99	$113.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3384				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	10
12"	24"	36"	48"	60"	72"	Custom Len.	
$119.99	$119.99	$121.99	$125.99	$127.99	$129.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3370				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	11
12"	24"	36"	48"	60"	72"	Custom Len.	
$125.99	$133.99	$143.99	$151.99	$161.99	$169.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3816				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	12
12"	24"	36"	48"	60"	72"	Custom Len.	
$80.99	$83.99	$87.99	$91.99	$94.99	$107.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3842				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	13
12"	24"	36"	48"	60"	72"	Custom Len.	
$107.99	$111.99	$107.99	$111.99	$115.99	$117.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3389				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	14
12"	24"	36"	48"	60"	72"	Custom Len.	
$94.99	$97.99	$101.99	$97.99	$109.99	$105.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3458				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	15
12"	24"	36"	48"	60"	72"	Custom Len.	
$93.99	$103.99	$111.99	$119.99	$127.99	$135.99	See Web	

PE-B100 Coax, 50 Ohm

Part No. PE38249				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.101" dia.			16
12"	24"	36"	48"	60"	-	Custom Len.	
$83.99	$91.99	$101.99	$109.99	$117.99	-	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE37640				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	17
12"	24"	36"	48"	60"	-	Custom Len.	
$84.99	$95.99	$107.99	$117.99	$127.99	-	See Web	

RG55B/U Coax, 53 Ohm

Part No. PE38506				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	18
12"	24"	36"	48"	60"	-	Custom Len.	
$71.99	$74.99	$77.99	$79.99	$82.99	-	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3935				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	19
12"	24"	36"	48"	60"	72"	Custom Len.	
$80.99	$81.99	$82.99	$83.99	$84.99	$85.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE3366				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	20
12"	24"	36"	48"	60"	72"	Custom Len.	
$90.99	$93.99	$96.99	$99.99	$103.99	$105.99	See Web	

BNC MALE RIGHT ANGLE TO BNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE33189				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	21
12"	24"	36"	48"	60"	-	Custom Len.	
$77.99	$78.99	$79.99	$77.99	$81.99	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C3314				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	22
12"	24"	36"	48"	60"	50CM	Custom Len.	
$87.99	$93.99	$103.99	$111.99	$119.99	$90.99	See Web	

BNC MALE RIGHT ANGLE TO SMA FEMALE



Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W04854				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	23
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.99	$72.99	$76.99	$80.99	$84.99	$70.99	See Web	

BNC MALE RIGHT ANGLE TO TNC MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

LMR-240-UF Coax, 50 Ohm

Part No. PE3W07480				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft		24
36"	48"	100CM	200CM	-	-	Custom Len.	
$86.99	$88.99	$87.99	$92.99	-	-	See Web	

BNC FEMALE TO BNC MALE RIGHT ANGLE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W06649				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	25
12"	24"	36"	48"	60"	50CM	Custom Len.	
$107.99	$107.99	$109.99	$109.99	$109.99	$107.99	See Web	

BNC FEMALE TO BNC FEMALE



Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE36345				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	26
12"	24"	36"	48"	60"	-	Custom Len.	
$131.99	$135.99	$137.99	$141.99	$145.99	-	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3052				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	27
12"	24"	36"	48"	60"	72"	Custom Len.	
$48.79	$49.79	$55.99	$56.99	$52.99	$58.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3088				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		28
12"	24"	36"	48"	60"	72"	Custom Len.	
$46.79	$53.99	$60.99	$72.99	$73.99	$80.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3604				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	29
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.99	$65.99	$65.99	$66.99	$64.99	$68.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36455				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	30
12"	24"	36"	48"	60"	-	Custom Len.	
$90.99	$85.99	$93.99	$94.99	$88.99	-	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3094				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	31
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.99	$74.99	$70.99	$73.99	$75.99	$78.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3953				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	32
12"	24"	36"	48"	60"	72"	Custom Len.	
$143.99	$153.99	$161.99	$171.99	$179.99	$189.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

RG223/U Coax, 50 Ohm

Part No. PE3364				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	33
12"	24"	36"	48"	60"	72"	Custom Len.	
$43.59	$47.19	$50.99	$59.99	$58.99	$61.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3505				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	34
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.99	$69.99	$79.99	$83.99	$80.99	$84.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3675				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	35
12"	24"	36"	48"	60"	72"	Custom Len.	
$29.59	$30.79	$30.99	$32.19	$33.19	$34.19	See Web	

BNC FEMALE TO NMO MOUNT SEXLESS



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37845				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	36
60"	120"	180"	-	-	-	Custom Len.	
$51.99	$56.99	$60.99	-	-	-	See Web	

BNC FEMALE BULKHEAD TO SMA MALE

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W03377				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.		121.5 W	37
12"	24"	36"	48"	60"	50CM	Custom Len.	
$93.99	$105.99	$115.99	$125.99	$135.99	$101.99	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3W01634				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	80 W	38
12"	24"	36"	48"	60"	50CM	Custom Len.	
$41.99	$43.19	$44.19	$45.19	$46.39	$42.79	See Web	

C MALE TO C MALE



Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE33316				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	39
12"	24"	36"	48"	60"	72"	Custom Len.	
$123.99	$133.99	$129.99	$133.99	$137.99	$139.99	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3457				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	40
12"	24"	36"	48"	60"	72"	Custom Len.	
$113.99	$113.99	$123.99	$115.99	$117.99	$117.99	See Web	

RG141A/U Coax, 50 Ohm

Part No. PE34440				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W	41
12"	24"	36"	48"	60"	72"	Custom Len.	
$101.99	$109.99	$117.99	$123.99	$131.99	$139.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3518				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	42
12"	24"	36"	48"	60"	72"	Custom Len.	
$92.99	$99.99	$107.99	$113.99	$121.99	$125.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3522				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	43
12"	24"	36"	48"	60"	72"	Custom Len.	
$121.99	$121.99	$123.99	$125.99	$127.99	$129.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3605				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	44
12"	24"	36"	48"	60"	72"	Custom Len.	
$111.99	$119.99	$135.99	$137.99	$145.99	$165.99	See Web	

RG217/U Coax, 50 Ohm

Part No. PE34437				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.	5.8 dB/100ft	260 W	45
12"	24"	36"	48"	60"	72"	Custom Len.	
$187.99	$191.99	$197.99	$203.99	$221.99	$213.99	See Web	

RG218/U Coax, 50 Ohm

Part No. PE34442				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.87" dia.	3.8 dB/100ft	560 W	46
12"	24"	36"	48"	60"	72"	Custom Len.	
$285.99	$299.99	$313.99	$327.99	$341.99	$355.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3343				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	47
12"	24"	36"	48"	60"	72"	Custom Len.	
$88.99	$92.99	$95.99	$99.99	$103.99	$107.99	See Web	

RG225/U Coax, 50 Ohm

Part No. PE33098				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.	7.5 dB/100ft	1,700 W	48
12"	24"	36"	48"	60"	72"	Custom Len.	
$135.99	$175.99	$215.99	$255.99	$295.99	$335.99	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3120				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	49
12"	24"	36"	48"	60"	72"	Custom Len.	
$121.99	$149.99	$169.99	$179.99	$211.99	$231.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3545				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	50
12"	24"	36"	48"	60"	72"	Custom Len.	
$94.99	$103.99	$111.99	$121.99	$127.99	$135.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE33662				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	51
12"	24"	36"	48"	60"	72"	Custom Len.	
$121.99	$121.99	$121.99	$121.99	$123.99	$125.99	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE34435				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	52
12"	24"	36"	48"	60"	72"	Custom Len.	
$123.99	$123.99	$125.99	$127.99	$127.99	$129.99	See Web	

C MALE RIGHT ANGLE TO C MALE



Standard Flexible Cable Assemblies

RG214/U Coax, 50 Ohm

Part No. PE3W08103				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	53
24"	36"	60"	-	-	-	Custom Len.	
$187.99	$197.99	$215.99	-	-	-	See Web	

D-SUB RECEPTACLE TO BNC MALE



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W01818				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		54
12"	24"	36"	48"	60"	50CM	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

FAKRA PLUG TO FAKRA PLUG



Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38747A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		55
12"	24"	36"	48"	60"	-	Custom Len.	
$28.79	$29.59	$30.59	$31.59	$32.39	-	See Web	
Part No. PE38747C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		56
12"	24"	36"	48"	60"	-	Custom Len.	
$29.19	$32.59	$33.39	$35.79	$38.39	-	See Web	
Part No. PE38747D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		57
12"	24"	36"	48"	60"	-	Custom Len.	
$30.19	$31.99	$34.59	$37.19	$39.79	-	See Web	
Part No. PE38747H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		58
12"	24"	36"	48"	60"	-	Custom Len.	
$28.79	$29.59	$30.59	$31.59	$32.39	-	See Web	
Part No. PE38747I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		59
12"	24"	36"	48"	60"	-	Custom Len.	
$30.19	$31.99	$34.59	$37.19	$39.79	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

Part No. PE38747K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		60
12"	24"	36"	48"	60"	-	Custom Len.	
$30.19	$31.99	$34.59	$37.19	$39.79	-	See Web	
Part No. PE38747Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		61
12"	24"	36"	48"	60"	-	Custom Len.	
$34.99	$33.99	$35.59	$40.19	$41.99	-	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE38751A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	62
12"	24"	36"	48"	60"	-	Custom Len.	
$33.99	$34.59	$35.19	$35.99	$36.59	-	See Web	
Part No. PE38751C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	63
12"	24"	36"	48"	60"	-	Custom Len.	
$37.39	$34.59	$35.19	$35.99	$36.59	-	See Web	
Part No. PE38751D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	64
12"	24"	36"	48"	60"	-	Custom Len.	
$33.99	$34.59	$35.19	$35.99	$36.59	-	See Web	
Part No. PE38751H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	65
12"	24"	36"	48"	60"	-	Custom Len.	
$33.99	$34.59	$35.19	$35.99	$36.59	-	See Web	
Part No. PE38751I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	66
12"	24"	36"	48"	60"	-	Custom Len.	
$33.99	$34.59	$35.19	$35.99	$36.59	-	See Web	
Part No. PE38751K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	67
12"	24"	36"	48"	60"	-	Custom Len.	
$33.99	$34.59	$35.19	$35.99	$36.59	-	See Web	
Part No. PE38751Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	68
12"	24"	36"	48"	60"	-	Custom Len.	
$40.99	$37.79	$38.39	$38.99	$43.99	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE38755A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	69
12"	24"	36"	48"	60"	-	Custom Len.	
$36.59	$40.19	$43.79	$47.39	$50.99	-	See Web	
Part No. PE38755C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	70
12"	24"	36"	48"	60"	-	Custom Len.	
$38.79	$38.59	$42.19	$45.59	$49.19	-	See Web	
Part No. PE38755D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	71
12"	24"	36"	48"	60"	-	Custom Len.	
$36.59	$40.19	$43.79	$47.39	$50.99	-	See Web	
Part No. PE38755H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	72
12"	24"	36"	48"	60"	-	Custom Len.	
$36.59	$40.19	$43.79	$47.39	$50.99	-	See Web	
Part No. PE38755I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	73
12"	24"	36"	48"	60"	-	Custom Len.	
$36.59	$40.19	$43.79	$47.39	$50.99	-	See Web	
Part No. PE38755K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	74
12"	24"	36"	48"	60"	-	Custom Len.	
$36.59	$40.19	$43.79	$47.39	$50.99	-	See Web	
Part No. PE38755Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	75
12"	24"	36"	48"	60"	-	Custom Len.	
$36.59	$40.19	$43.79	$52.99	$50.99	-	See Web	

FAKRA PLUG TO FAKRA JACK



Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38748A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		76
12"	24"	36"	48"	60"	-	Custom Len.	
$32.39	$33.99	$35.59	$37.19	$42.59	-	See Web	
Part No. PE38748C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		77
12"	24"	36"	48"	60"	-	Custom Len.	
$35.59	$33.99	$38.99	$37.19	$42.59	-	See Web	

Part No. PE38748D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		78
12"	24"	36"	48"	60"	-	Custom Len.	
$32.39	$33.99	$35.59	$37.19	$42.59	-	See Web	
Part No. PE38748H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		79
12"	24"	36"	48"	60"	-	Custom Len.	
$32.39	$33.99	$35.59	$37.19	$39.79	-	See Web	
Part No. PE38748I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		80
12"	24"	36"	48"	60"	-	Custom Len.	
$30.19	$31.99	$34.59	$37.19	$39.79	-	See Web	
Part No. PE38748K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		81
12"	24"	36"	48"	60"	-	Custom Len.	
$32.39	$33.99	$38.39	$37.19	$41.99	-	See Web	
Part No. PE38748Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		82
12"	24"	36"	48"	60"	-	Custom Len.	
$34.39	$36.19	$37.79	$39.59	$41.39	-	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE38752A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	83
12"	24"	36"	48"	60"	-	Custom Len.	
$37.39	$37.79	$38.39	$38.99	$39.59	-	See Web	
Part No. PE38752C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	84
12"	24"	36"	48"	60"	-	Custom Len.	
$37.39	$37.79	$38.39	$38.99	$43.99	-	See Web	
Part No. PE38752D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	85
12"	24"	36"	48"	60"	-	Custom Len.	
$37.39	$37.79	$38.39	$42.59	$39.59	-	See Web	
Part No. PE38752H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	86
12"	24"	36"	48"	60"	-	Custom Len.	
$37.39	$37.79	$38.39	$38.99	$43.19	-	See Web	
Part No. PE38752I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	87
12"	24"	36"	48"	60"	-	Custom Len.	
$37.39	$37.79	$38.39	$38.99	$43.99	-	See Web	
Part No. PE38752K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	88
12"	24"	36"	48"	60"	-	Custom Len.	
$36.59	$40.19	$37.79	$41.79	$38.79	-	See Web	
Part No. PE38752Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	89
12"	24"	36"	48"	60"	-	Custom Len.	
$39.59	$40.19	$40.99	$41.79	$42.59	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE38756A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	90
12"	24"	36"	48"	60"	-	Custom Len.	
$36.59	$40.19	$43.79	$47.39	$50.99	-	See Web	
Part No. PE38756B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	91
12"	24"	36"	48"	60"	-	Custom Len.	
$40.19	$43.99	$47.59	$51.99	$54.99	-	See Web	
Part No. PE38756C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	92
12"	24"	36"	48"	60"	-	Custom Len.	
$40.19	$43.99	$47.59	$51.99	$54.99	-	See Web	
Part No. PE38756D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	93
12"	24"	36"	48"	60"	-	Custom Len.	
$36.59	$40.19	$43.79	$47.39	$50.99	-	See Web	
Part No. PE38756H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	94
12"	24"	36"	48"	60"	-	Custom Len.	
$36.59	$40.19	$43.79	$47.39	$50.99	-	See Web	
Part No. PE38756I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	95
12"	24"	36"	48"	60"	-	Custom Len.	
$36.59	$40.19	$43.79	$47.39	$56.99	-	See Web	
Part No. PE38756K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	96
12"	24"	36"	48"	60"	-	Custom Len.	
$40.19	$43.99	$47.59	$51.99	$54.99	-	See Web	
Part No. PE38756Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	97
12"	24"	36"	48"	60"	-	Custom Len.	
$44.39	$48.19	$52.99	$51.99	$60.99	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

FAKRA PLUG TO FAKRA JACK RIGHT ANGLE



Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38749A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		98
12"	24"	36"	48"	60"	-	Custom Len.	
$31.99	$33.59	$36.39	$38.79	$41.59	-	See Web	

Part No. PE38749B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		99
12"	24"	36"	48"	60"	-	Custom Len.	
$32.19	$30.19	$30.99	$31.99	$31.99	-	See Web	

Part No. PE38749C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		1
12"	24"	36"	48"	60"	-	Custom Len.	
$31.99	$33.59	$36.39	$39.39	$41.59	-	See Web	

Part No. PE38749D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		2
12"	24"	36"	48"	60"	-	Custom Len.	
$32.59	$34.19	$35.79	$37.19	$38.79	-	See Web	

Part No. PE38749H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		3
12"	24"	36"	48"	60"	-	Custom Len.	
$29.39	$30.19	$30.99	$31.99	$31.99	-	See Web	

Part No. PE38749I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		4
12"	24"	36"	48"	60"	-	Custom Len.	
$29.39	$30.19	$30.99	$31.99	$31.99	-	See Web	

Part No. PE38749K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		5
12"	24"	36"	48"	60"	-	Custom Len.	
$32.59	$34.19	$35.79	$37.19	$38.79	-	See Web	

Part No. PE38749Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		6
12"	24"	36"	48"	60"	-	Custom Len.	
$34.19	$35.79	$37.39	$38.99	$41.59	-	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE38753A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	7
12"	24"	36"	48"	60"	-	Custom Len.	
$42.19	$42.99	$43.59	$44.19	$44.99	-	See Web	

Part No. PE38753C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	8
12"	24"	36"	48"	60"	-	Custom Len.	
$45.59	$46.19	$46.79	$47.39	$52.99	-	See Web	

Part No. PE38753D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	9
12"	24"	36"	48"	60"	-	Custom Len.	
$42.19	$42.99	$43.59	$44.19	$44.99	-	See Web	

Part No. PE38753H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	10
12"	24"	36"	48"	60"	-	Custom Len.	
$46.59	$46.99	$47.59	$48.19	$48.79	-	See Web	

Part No. PE38753I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	11
12"	24"	36"	48"	60"	-	Custom Len.	
$42.19	$42.99	$43.59	$44.19	$44.99	-	See Web	

Part No. PE38753K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	12
12"	24"	36"	48"	60"	-	Custom Len.	
$42.19	$42.99	$43.59	$44.19	$44.99	-	See Web	

Part No. PE38753Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	13
12"	24"	36"	48"	60"	-	Custom Len.	
$50.99	$50.99	$47.59	$48.19	$48.79	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE38757A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	14
12"	24"	36"	48"	60"	-	Custom Len.	
$44.79	$48.39	$52.99	$55.99	$59.99	-	See Web	

Part No. PE38757C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	15
12"	24"	36"	48"	60"	-	Custom Len.	
$44.79	$48.39	$52.99	$55.99	$59.99	-	See Web	

Part No. PE38757D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	16
12"	24"	36"	48"	60"	-	Custom Len.	
$44.79	$48.39	$52.99	$55.99	$59.99	-	See Web	

Part No. PE38757H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	17
12"	24"	36"	48"	60"	-	Custom Len.	
$44.79	$48.39	$52.99	$55.99	$59.99	-	See Web	

Part No. PE38757I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	18
12"	24"	36"	48"	60"	-	Custom Len.	
$44.79	$48.39	$52.99	$55.99	$59.99	-	See Web	

Part No. PE38757K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	19
12"	24"	36"	48"	60"	-	Custom Len.	
$44.79	$48.39	$52.99	$55.99	$59.99	-	See Web	

FAKRA PLUG TO SMA MALE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C6275				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	20
12"	-	-	-	-	-	Custom Len.	
Call	-	-	-	-	-	See Web	

FAKRA JACK TO FAKRA JACK



Standard Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38746A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft	40 W	21
12"	24"	36"	48"	60"	-	Custom Len.	
$35.59	$37.39	$35.59	$37.19	$39.79	-	See Web	

Part No. PE38746Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft	40 W	22
12"	24"	36"	48"	60"	-	Custom Len.	
$31.59	$32.39	$34.19	$35.99	$37.59	-	See Web	

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38746B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		23
12"	24"	36"	48"	60"	-	Custom Len.	
$34.99	$36.79	$35.59	$37.19	$41.99	-	See Web	

Part No. PE38746C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		24
12"	24"	36"	48"	60"	-	Custom Len.	
$35.59	$37.39	$35.59	$40.79	$42.59	-	See Web	

Part No. PE38746D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		25
12"	24"	36"	48"	60"	-	Custom Len.	
$32.39	$33.99	$38.39	$40.19	$39.79	-	See Web	

Part No. PE38746H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		26
12"	24"	36"	48"	60"	-	Custom Len.	
$28.79	$29.59	$30.59	$31.59	$32.39	-	See Web	

Part No. PE38746I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		27
12"	24"	36"	48"	60"	-	Custom Len.	
$32.39	$33.99	$38.99	$37.19	$42.59	-	See Web	

Part No. PE38746K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		28
12"	24"	36"	48"	60"	-	Custom Len.	
$32.39	$33.99	$35.59	$40.79	$39.79	-	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE38750A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	29
12"	24"	36"	48"	60"	-	Custom Len.	
$37.39	$37.79	$42.39	$38.99	$39.59	-	See Web	

Part No. PE38750B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	30
12"	24"	36"	48"	60"	-	Custom Len.	
$33.99	$34.59	$37.99	$35.99	$36.59	-	See Web	

Part No. PE38750C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	31
12"	24"	36"	48"	60"	-	Custom Len.	
$37.39	$37.79	$40.99	$38.99	$42.59	-	See Web	

Part No. PE38750D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	32
12"	24"	36"	48"	60"	-	Custom Len.	
$37.39	$37.79	$41.79	$38.99	$43.19	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

Part No. PE38750H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	33
12"	24"	36"	48"	60"	-	Custom Len.	
$36.59	$40.19	$37.79	$41.79	$38.79	-	See Web	

Part No. PE38750I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	34
12"	24"	36"	48"	60"	-	Custom Len.	
$33.99	$34.59	$35.19	$35.99	$36.59	-	See Web	

Part No. PE38750K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	35
12"	24"	36"	48"	60"	-	Custom Len.	
$37.39	$40.99	$38.39	$38.99	$39.59	-	See Web	

Part No. PE38750Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	36
12"	24"	36"	48"	60"	-	Custom Len.	
$37.39	$38.19	$38.79	$39.59	$40.39	-	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE3W02209				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	37
12"	24"	36"	48"	60"	50CM	Custom Len.	
$38.39	$42.79	$46.99	$51.99	$55.99	$41.19	See Web	

RG316/U Coax, 50 Ohm

Part No. PE38754A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	38
12"	24"	36"	48"	60"	-	Custom Len.	
$40.19	$43.99	$47.59	$51.99	$54.99	-	See Web	

Part No. PE38754B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	39
12"	24"	36"	48"	60"	-	Custom Len.	
$36.59	$40.19	$43.79	$47.39	$50.99	-	See Web	

Part No. PE38754C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	40
12"	24"	36"	48"	60"	-	Custom Len.	
$38.79	$42.79	$46.59	$47.39	$50.99	-	See Web	

Part No. PE38754D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	41
12"	24"	36"	48"	60"	-	Custom Len.	
$40.19	$44.19	$43.79	$47.39	$50.99	-	See Web	

Part No. PE38754H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	42
12"	24"	36"	48"	60"	-	Custom Len.	
$36.59	$40.19	$46.59	$47.39	$50.99	-	See Web	

Part No. PE38754I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	43
12"	24"	36"	48"	60"	-	Custom Len.	
$36.59	$40.19	$43.79	$47.39	$50.99	-	See Web	

Part No. PE38754K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	44
12"	24"	36"	48"	60"	-	Custom Len.	
$36.59	$40.19	$43.79	$47.39	$50.99	-	See Web	

Part No. PE38754Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		45
12"	24"	36"	48"	60"	-	Custom Len.	
$40.79	$44.59	$48.59	$52.99	$56.99	-	See Web	

FAKRA JACK TO FAKRA JACK RIGHT ANGLE



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W02943				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		46
12"	24"	36"	48"	60"	50CM	Custom Len.	
$31.39	$32.39	$32.39	$33.39	$34.39	$31.99	See Web	

FAKRA JACK TO SMA FEMALE



Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE39351Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		47
12"	24"	36"	48"	60"	-	Custom Len.	
$70.99	$67.99	$71.99	$75.99	$78.99	-	See Web	

FAKRA JACK TO REVERSE POLARITY TNC MALE



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W03361				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		48
12"	24"	36"	48"	60"	50CM	Custom Len.	
$51.99	$52.99	$53.99	$54.99	$55.99	$52.99	See Web	

FAKRA JACK RIGHT ANGLE TO FAKRA PLUG



Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE38757Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		49
12"	24"	36"	48"	60"	-	Custom Len.	
$54.99	$52.99	$56.99	$60.99	$63.99	-	See Web	

FME PLUG TO BNC MALE



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE35959				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	50
12"	24"	36"	48"	60"	72"	Custom Len.	
$50.99	$51.99	$52.99	$53.99	$54.99	$55.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE35962				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	51
12"	24"	36"	48"	60"	72"	Custom Len.	
$43.39	$50.99	$57.99	$63.99	$70.99	$77.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3420				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	52
12"	24"	36"	48"	60"	72"	Custom Len.	
$46.19	$46.79	$47.39	$47.79	$48.39	$48.99	See Web	

FME PLUG TO FME PLUG



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38719				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	53
12"	24"	36"	48"	60"	-	Custom Len.	
$45.99	$46.99	$47.79	$48.79	$49.59	-	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE35953				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	54
12"	24"	36"	48"	60"	72"	Custom Len.	
$51.99	$52.99	$53.99	$54.99	$55.99	$56.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE35955				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	55
12"	24"	36"	48"	60"	72"	Custom Len.	
$48.19	$55.99	$61.99	$68.99	$75.99	$81.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE35957				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	56
12"	24"	36"	48"	60"	72"	Custom Len.	
$50.99	$51.99	$51.99	$52.99	$53.99	$53.99	See Web	

FME PLUG TO NMO MOUNT SEXLESS



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37842				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	57
60"	120"	180"	-	-	-	Custom Len.	
$55.99	$59.99	$63.99	-	-	-	See Web	

FME PLUG BULKHEAD TO UMCX PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Flexible Cable Assemblies

PE-113mm Coax, 50 Ohm

Part No. PE38858				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.044" dia.			58
6"	12"	18"	-	-	-	Custom Len.	
$39.19	Call	Call	-	-	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

FME JACK TO BNC MALE



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE34862				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	59
12"	24"	36"	48"	60"	72"	Custom Len.	
$41.39	$42.19	$43.19	$44.19	$44.99	$45.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE34864				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	60
12"	24"	36"	48"	60"	72"	Custom Len.	
$39.79	$46.59	$53.99	$60.99	$66.99	$73.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3409				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	61
12"	24"	36"	48"	60"	72"	Custom Len.	
$46.39	$46.99	$47.59	$47.99	$48.59	$49.19	See Web	

FME JACK TO FME JACK



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE34856				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	62
12"	24"	36"	48"	60"	72"	Custom Len.	
$47.19	$48.19	$48.99	$49.99	$50.99	$51.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE34858				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	63
12"	24"	36"	48"	60"	72"	Custom Len.	
$40.59	$47.59	$54.99	$60.99	$67.99	$74.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE34860				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	64
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.99	$51.99	$52.99	$52.99	$53.99	$54.99	See Web	

FME JACK TO NMO MOUNT SEXLESS



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37843				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	65
60"	120"	180"	-	-	-	Custom Len.	
$50.99	$55.99	$59.99	-	-	-	See Web	

GR874 SEXLESS TO BNC MALE



Standard Flexible Cable Assemblies

RG214/U Coax, 50 Ohm

Part No. PE3145				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	66
12"	24"	36"	48"	60"	72"	Custom Len.	
$169.99	$179.99	$187.99	$197.99	$205.99	$215.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3182				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	67
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.99	$64.99	$68.99	$71.99	$75.99	$78.99	See Web	

GR874 SEXLESS TO GR874 SEXLESS



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3211				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	68
12"	24"	36"	48"	60"	72"	Custom Len.	
$91.99	$92.99	$93.99	$94.99	$95.99	$96.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3200				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		69
12"	24"	36"	48"	60"	72"	Custom Len.	
$90.99	$96.99	$103.99	$111.99	$117.99	$123.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3158				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	70
12"	24"	36"	48"	60"	72"	Custom Len.	
$251.99	$259.99	$269.99	$277.99	$287.99	$295.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3190				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	71
12"	24"	36"	48"	60"	72"	Custom Len.	
$92.99	$95.99	$99.99	$103.99	$107.99	$109.99	See Web	

HN MALE TO 7/16 DIN MALE RIGHT ANGLE



Standard Flexible Cable Assemblies

RG217/U Coax, 50 Ohm

Part No. PE3W03391				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.	5.8 dB/100ft	260 W	72
12"	24"	36"	48"	60"	50CM	Custom Len.	
$317.99	$323.99	$329.99	$335.99	$341.99	$321.99	See Web	

HN MALE TO HN MALE



Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE33304				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	73
12"	24"	36"	48"	60"	72"	Custom Len.	
$139.99	$143.99	$155.99	$159.99	$153.99	$157.99	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3852				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	74
12"	24"	36"	48"	60"	72"	Custom Len.	
$107.99	$109.99	$109.99	$111.99	$111.99	$113.99	See Web	

RG141A/U Coax, 50 Ohm

Part No. PE34434				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W	75
12"	24"	36"	48"	60"	72"	Custom Len.	
$117.99	$123.99	$131.99	$139.99	$147.99	$153.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3083				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		76
12"	24"	36"	48"	60"	72"	Custom Len.	
$111.99	$119.99	$131.99	$139.99	$139.99	$155.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3038				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	9 dB/100ft	190 W	77
12"	24"	36"	48"	60"	72"	Custom Len.	
$143.99	$145.99	$147.99	$149.99	$151.99	$153.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3095				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	78
12"	24"	36"	48"	60"	72"	Custom Len.	
$153.99	$153.99	$163.99	$183.99	$193.99	$201.99	See Web	

RG217/U Coax, 50 Ohm

Part No. PE33370				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.	5.8 dB/100ft	260 W	79
12"	24"	36"	48"	60"	72"	Custom Len.	
$153.99	$159.99	$165.99	$171.99	$177.99	$183.99	See Web	

RG218/U Coax, 50 Ohm

Part No. PE33583				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.87" dia.	3.8 dB/100ft	560 W	80
12"	24"	36"	48"	60"	72"	Custom Len.	
$347.99	$361.99	$375.99	$389.99	$403.99	$417.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3357				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	81
12"	24"	36"	48"	60"	72"	Custom Len.	
$109.99	$119.99	$121.99	$119.99	$129.99	$125.99	See Web	

RG225/U Coax, 50 Ohm

Part No. PE33778				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	82
12"	24"	36"	48"	60"	72"	Custom Len.	
$179.99	$221.99	$261.99	$303.99	$345.99	$385.99	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3340				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	83
12"	24"	36"	48"	60"	72"	Custom Len.	
$161.99	$171.99	$201.99	$221.99	$243.99	$263.99	See Web	

For our complete selection of cable assemblies, please visit our website

RG400/U Coax, 50 Ohm

Part No. PE33938				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	84
12"	24"	36"	48"	60"	72"	Custom Len.	
$127.99	$129.99	$137.99	$145.99	$153.99	$163.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE34436				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	85
12"	24"	36"	48"	60"	72"	Custom Len.	
$135.99	$137.99	$137.99	$139.99	$139.99	$141.99	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE34438				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	86
12"	24"	36"	48"	60"	72"	Custom Len.	
$139.99	$139.99	$141.99	$143.99	$145.99	$147.99	See Web	

HN MALE RIGHT ANGLE TO HN FEMALE



Standard Flexible Cable Assemblies

RG213/U Coax, 50 Ohm

Part No. PE3W05081				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.		190 W	87
12"	24"	36"	48"	60"	50CM	Custom Len.	
$165.99	$167.99	$169.99	$173.99	$175.99	$167.99	See Web	

LC MALE TO LC MALE



Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE33541				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	88
60"	72"	84"	96"	108"	120"	Custom Len.	
$477.99	$483.99	$491.99	$497.99	$505.00	$515.00	See Web	

RG214/U Coax, 50 Ohm

Part No. PE33491				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	89
60"	72"	84"	96"	108"	120"	Custom Len.	
$433.99	$443.99	$451.99	$461.99	$469.99	$479.99	See Web	

RG217/U Coax, 50 Ohm

Part No. PE33537				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.	5.8 dB/100ft	260 W	90
60"	72"	84"	96"	108"	120"	Custom Len.	
$487.99	$493.99	$499.99	$505.00	$510.00	$515.00	See Web	

RG218/U Coax, 50 Ohm

Part No. PE3960				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.87" dia.	3.8 dB/100ft	560 W	91
60"	72"	84"	96"	108"	120"	Custom Len.	
$660.00	$635.00	$650.00	$665.00	$680.00	$690.00	See Web	

RG225/U Coax, 50 Ohm

Part No. PE34538				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	92
60"	72"	84"	96"	108"	120"	Custom Len.	
$595.00	$635.00	$675.00	$715.00	$755.00	$795.00	See Web	

RG393/U Coax, 50 Ohm

Part No. PE33539				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	93
60"	72"	84"	96"	108"	120"	Custom Len.	
$545.00	$565.00	$550.00	$610.00	$590.00	$610.00	See Web	

LC MALE RIGHT ANGLE TO HN MALE



Standard Flexible Cable Assemblies

RG393/U Coax, 50 Ohm

Part No. PE3W00314				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.		1,700 W	94
12"	24"	36"	48"	60"	50CM	Custom Len.	
$373.99	$391.99	$411.99	$431.99	$451.99	$385.99	See Web	

MC-CARD PLUG TO MC-CARD PLUG



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36114				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	95
12"	24"	36"	48"	60"	72"	Custom Len.	
$52.99	$53.99	$53.99	$54.99	$54.99	$55.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36116				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	96
12"	24"	36"	48"	60"	72"	Custom Len.	
$52.99	$53.99	$54.99	$55.99	$57.99	$58.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE36118				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	97
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.99	$59.99	$62.99	$66.99	$69.99	$73.99	See Web	

MC-CARD PLUG TO MC-CARD PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36120				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	98
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.99	$54.99	$54.99	$55.99	$55.99	$56.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36122				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	99
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.99	$62.99	$63.99	$64.99	$65.99	$66.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE36124				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	1
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.99	$60.99	$63.99	$67.99	$70.99	$74.99	See Web	

MC-CARD PLUG RIGHT ANGLE TO MC-CARD PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36126				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	2
12"	24"	36"	48"	60"	-	Custom Len.	
$54.99	$55.99	$55.99	$56.99	$56.99	-	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36128				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	3
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.99	$64.99	$65.99	$66.99	$67.99	$68.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE36130				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	4
12"	24"	36"	48"	60"	72"	Custom Len.	
$57.99	$61.99	$64.99	$67.99	$71.99	$75.99	See Web	

MCX PLUG TO BNC MALE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C3387				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	5
12"	50CM	24"	36"	100CM	48"	Custom Len.	
$49.19	$45.99	$46.39	$46.99	$47.19	$47.79	See Web	

MCX PLUG TO 75 OHM BNC MALE



Standard Flexible Cable Assemblies

RG187A/U Coax, 75 Ohm

Part No. PE3C5491				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	25 dB/100ft	200 W	6
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$60.99	$64.99	$69.99	$73.99	$58.99	See Web	

MCX PLUG TO MCX PLUG



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3295				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	7
12"	24"	36"	48"	60"	72"	Custom Len.	
$58.99	$59.99	$60.99	$60.99	$61.99	$61.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

***Coax Performance at 1 GHz** **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

RG188A/U Coax, 50 Ohm

Part No. PE3290				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	8
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.99	$62.99	$65.99	$68.99	$77.99	$74.99	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE3293				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	9
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.99	$70.99	$72.99	$74.99	$76.99	$77.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3297				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		10
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.99	$63.99	$67.99	$70.99	$79.99	$78.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE36799				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	11
12"	41CM	48CM	56CM	24"	36"	Custom Len.	
Call	Call	Call	Call	$60.99	$68.99	See Web	

MCX PLUG TO MCX PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3314				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	12
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.99	$62.99	$62.99	$63.99	$63.99	$64.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3309				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	13
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.99	$62.99	$64.99	$67.99	$70.99	$72.99	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE3311				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	14
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.99	$64.99	$66.99	$68.99	$69.99	$71.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3316				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		15
12"	24"	36"	48"	60"	72"	Custom Len.	
$65.99	$69.99	$72.99	$76.99	$79.99	$83.99	See Web	

MCX PLUG TO SMA MALE



Standard Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W06468				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		16
12"	24"	36"	48"	60"	50CM	Custom Len.	
$48.59	$48.59	$49.59	$50.99	$51.99	$48.39	See Web	

MCX PLUG TO TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W03310				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	17
12"	24"	36"	48"	60"	50CM	Custom Len.	
$103.99	$105.99	$105.99	$105.99	$107.99	$105.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3W05645				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		18
12"	24"	36"	48"	60"	50CM	Custom Len.	
$115.99	$119.99	$123.99	$125.99	$129.99	$117.99	See Web	

MCX PLUG RIGHT ANGLE TO BNC FEMALE 4 HOLE FLANGE

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Flexible Cable Assemblies

RG316-DS Coax, 50 Ohm

Part No. PE3W01570				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	19
12"	24"	36"	48"	60"	50CM	Custom Len.	
$91.99	$95.99	$99.99	$103.99	$107.99	$93.99	See Web	

MCX PLUG RIGHT ANGLE TO MCX PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3304				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	20
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.99	$62.99	$62.99	$63.99	$64.99	$64.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3299				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	21
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.99	$71.99	$73.99	$76.99	$79.99	$82.99	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE3301				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	22
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.99	$64.99	$65.99	$67.99	$69.99	$70.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3306				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		23
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.99	$74.99	$78.99	$81.99	$85.99	$88.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE37099				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	24
12"	24"	36"	48"	60"	-	Custom Len.	
$70.99	$73.99	$83.99	$80.99	$84.99	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE35463				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	25
12"	24"	36"	48"	60"	-	Custom Len.	
$80.99	$89.99	$97.99	$107.99	$115.99	-	See Web	

MCX PLUG RIGHT ANGLE TO MCX JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W01300				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	26
12"	24"	36"	48"	60"	50CM	Custom Len.	
$67.99	$76.99	$77.99	$78.99	$78.99	$76.99	See Web	

MCX PLUG RIGHT ANGLE TO SMA MALE



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W07396				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	27
12"	24"	36"	48"	60"	50CM	Custom Len.	
$117.99	$125.99	$137.99	$147.99	$157.99	$121.99	See Web	

MCX PLUG RIGHT ANGLE TO SMA FEMALE



Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3W08540				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		28
24"	48"	-	-	-	-	Custom Len.	
$61.99	$62.99	-	-	-	-	See Web	

MCX JACK TO MCX JACK



Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3W00099				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	29
12"	24"	36"	48"	60"	50CM	Custom Len.	
$84.99	$85.99	$87.99	$88.99	$90.99	$85.99	See Web	

MHV MALE TO MHV MALE



Standard Flexible Cable Assemblies

Continued on Next Page

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

RG8A/U Coax, 50 Ohm

Part No. PE3098				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W
12"	24"	36"	48"	60"	72"	Custom Len.
$119.99	$127.99	$123.99	$127.99	$139.99	$143.99	See Web

30

RG58C/U Coax, 50 Ohm

Part No. PE3516				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	72"	Custom Len.
$96.99	$97.99	$98.99	$99.99	$101.99	$101.99	See Web

31

RG141A/U Coax, 50 Ohm

Part No. PE34429				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W
12"	24"	36"	48"	60"	72"	Custom Len.
$107.99	$115.99	$129.99	$137.99	$147.99	$145.99	See Web

32

RG142B/U Coax, 50 Ohm

Part No. PE3914				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft	
12"	24"	36"	48"	60"	72"	Custom Len.
$73.99	$80.99	$87.99	$92.99	$101.99	$109.99	See Web

33

RG174A/U Coax, 50 Ohm

Part No. PE34427				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W
12"	24"	36"	48"	60"	72"	Custom Len.
$123.99	$123.99	$129.99	$123.99	$129.99	$131.99	See Web

34

RG188A/U Coax, 50 Ohm

Part No. PE34431				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$125.99	$127.99	$131.99	$133.99	$137.99	$139.99	See Web

35

RG214/U Coax, 50 Ohm

Part No. PE3735				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W
12"	24"	36"	48"	60"	72"	Custom Len.
$131.99	$131.99	$149.99	$149.99	$159.99	$167.99	See Web

36

RG223/U Coax, 50 Ohm

Part No. PE3694				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W
12"	24"	36"	48"	60"	72"	Custom Len.
$73.99	$73.99	$76.99	$85.99	$83.99	$93.99	See Web

37

Part No. PE3W08544				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W
18"	150CM	-	-	-	-	Custom Len.
$61.99	$73.99	-	-	-	-	See Web

38

RG225/U Coax, 50 Ohm

Part No. PE34423				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W
12"	24"	36"	48"	60"	72"	Custom Len.
$145.99	$185.99	$225.99	$265.99	$307.99	$347.99	See Web

39

RG316/U Coax, 50 Ohm

Part No. PE34433				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$119.99	$123.99	$125.99	$129.99	$131.99	$135.99	See Web

40

RG393/U Coax, 50 Ohm

Part No. PE3577				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W
12"	24"	36"	48"	60"	72"	Custom Len.
$133.99	$161.99	$171.99	$189.99	$209.99	$227.99	See Web

41

RG59B/U Coax, 75 Ohm

Part No. PE3542				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$56.99	$61.99	$63.99	$60.99	$65.99	$67.99	See Web

42

RG62A/U Coax, 93 Ohm

Part No. PE3517				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$61.99	$63.99	$65.99	$62.99	$64.99	$71.99	See Web

43

MHV MALE TO MHV MALE RIGHT ANGLE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE35799				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W
12"	24"	36"	48"	60"	-	Custom Len.
$127.99	$129.99	$129.99	$121.99	$123.99	-	See Web

44

MHV MALE TO SHV PLUG



Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3365				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W
12"	24"	36"	48"	60"	72"	Custom Len.
$121.99	$123.99	$125.99	$129.99	$133.99	$137.99	See Web

45

RG58C/U Coax, 50 Ohm

Part No. PE3950				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	72"	Custom Len.
$109.99	$119.99	$121.99	$113.99	$121.99	$123.99	See Web

46

RG141A/U Coax, 50 Ohm

Part No. PE34413				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W
12"	24"	36"	48"	60"	72"	Custom Len.
$117.99	$123.99	$145.99	$153.99	$147.99	$155.99	See Web

47

RG142B/U Coax, 50 Ohm

Part No. PE3085				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft	
12"	24"	36"	48"	60"	72"	Custom Len.
$109.99	$115.99	$121.99	$127.99	$135.99	$151.99	See Web

48

RG174A/U Coax, 50 Ohm

Part No. PE34419				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W
12"	24"	36"	48"	60"	72"	Custom Len.
$127.99	$123.99	$129.99	$123.99	$123.99	$123.99	See Web

49

RG188A/U Coax, 50 Ohm

Part No. PE34415				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$121.99	$123.99	$127.99	$129.99	$131.99	$135.99	See Web

50

RG214/U Coax, 50 Ohm

Part No. PE33516				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W
12"	24"	36"	48"	60"	72"	Custom Len.
$133.99	$133.99	$143.99	$151.99	$171.99	$169.99	See Web

51

RG223/U Coax, 50 Ohm

Part No. PE34411				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W
12"	24"	36"	48"	60"	72"	Custom Len.
$89.99	$92.99	$103.99	$99.99	$103.99	$115.99	See Web

52

RG225/U Coax, 50 Ohm

Part No. PE34407				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W
12"	24"	36"	48"	60"	72"	Custom Len.
$149.99	$189.99	$229.99	$269.99	$309.99	$351.99	See Web

53

RG316/U Coax, 50 Ohm

Part No. PE34417				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$123.99	$125.99	$129.99	$133.99	$137.99	$141.99	See Web

54

RG393/U Coax, 50 Ohm

Part No. PE33984				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W
12"	24"	36"	48"	60"	72"	Custom Len.
$135.99	$155.99	$173.99	$193.99	$211.99	$231.99	See Web

55

RG400/U Coax, 50 Ohm

Part No. PE34409				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W
12"	24"	36"	48"	60"	72"	Custom Len.
$95.99	$103.99	$113.99	$121.99	$127.99	$145.99	See Web

56

RG59B/U Coax, 75 Ohm

Part No. PE3108				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$91.99	$92.99	$86.99	$95.99	$89.99	$97.99	See Web

57

RG62A/U Coax, 93 Ohm

Part No. PE3451				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$85.99	$86.99	$88.99	$90.99	$92.99	$93.99	See Web

58

MINI UHF MALE TO MINI UHF MALE



Standard Flexible Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

***Coax Performance at 1 GHz** **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

RG58C/U Coax, 50 Ohm

Part No. PE3258				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	59
12"	24"	36"	48"	60"	72"	Custom Len.	
$40.19	$40.99	$41.99	$42.99	$48.39	$44.79	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3263				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		60
12"	24"	36"	48"	60"	72"	Custom Len.	
$39.99	$43.99	$50.99	$57.99	$64.99	$70.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3265				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	61
12"	24"	36"	48"	60"	72"	Custom Len.	
$33.79	$37.39	$44.99	$44.79	$48.39	$51.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3269				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	62
12"	24"	36"	48"	60"	72"	Custom Len.	
$46.39	$55.99	$63.99	$71.99	$80.99	$89.99	See Web	

MINI UHF MALE TO NMO MOUNT SEXLESS



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37846				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	63
60"	120"	180"	-	-	-	Custom Len.	
$51.99	$56.99	$60.99	-	-	-	See Web	

MINI UHF FEMALE TO NMO MOUNT SEXLESS



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37847				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	64
60"	120"	180"	-	-	-	Custom Len.	
$55.99	$60.99	$64.99	-	-	-	See Web	

MMCX PLUG TO MMCX PLUG



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE34879				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	65
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.99	$68.99	$74.99	$69.99	$70.99	$70.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE34598				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	66
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.99	$74.99	$68.99	$70.99	$71.99	$72.99	See Web	
Part No. PE34599				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	67
4"	-	-	-	-	-	Custom Len.	
$109.99	-	-	-	-	-	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34885				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	68
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.99	$66.99	$68.99	$71.99	$73.99	$76.99	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE34891				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	69
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.99	$63.99	$64.99	$66.99	$67.99	$69.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34240				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		70
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.99	$74.99	$78.99	$81.99	$85.99	$88.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE38679				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	71
12"	24"	36"	48"	60"	-	Custom Len.	
$63.99	$67.99	$70.99	$74.99	$78.99	-	See Web	

MMCX PLUG TO MMCX PLUG RIGHT ANGLE



Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38231				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		72
12"	24"	36"	48"	60"	-	Custom Len.	
$62.99	$63.99	$65.99	$66.99	$68.99	-	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE38322				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	73
12"	24"	36"	48"	60"	-	Custom Len.	
$101.99	$105.99	$113.99	$121.99	$129.99	-	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE34881				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	74
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.99	$78.99	$73.99	$73.99	$74.99	$74.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE34883				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	75
12"	24"	36"	48"	60"	72"	Custom Len.	
$76.99	$78.99	$79.99	$80.99	$81.99	$82.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34889				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	76
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.99	$84.99	$79.99	$81.99	$84.99	$87.99	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE34893				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	77
12"	24"	36"	48"	60"	72"	Custom Len.	
$71.99	$72.99	$74.99	$75.99	$77.99	$79.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34895				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	78
12"	24"	36"	48"	60"	72"	Custom Len.	
$82.99	$86.99	$81.99	$85.99	$89.99	$92.99	See Web	

MMCX PLUG TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE3W07591				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					36 dB/100ft	32 W	79
12"	24"	36"	48"	60"	50CM	Custom Len.	
$107.99	$117.99	$127.99	$137.99	$147.99	$113.99	See Web	

MMCX PLUG TO SMC PLUG



Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3W07653				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	80
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$61.99	$62.99	$64.99	$65.99	$60.99	See Web	

MMCX PLUG RIGHT ANGLE TO BNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36738				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	81
12"	24"	36"	48"	60"	-	Custom Len.	
$73.99	$73.99	$74.99	$70.99	$76.99	-	See Web	

MMCX PLUG RIGHT ANGLE TO MMCX PLUG



Standard Formable Cable Assemblies

Continued on Next Page

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W05483				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	82
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.99	$89.99	$101.99	$111.99	$121.99	$85.99	See Web	

MMCX PLUG RIGHT ANGLE TO N FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39450					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22.5 dB/100ft	105 W	83
6"	9"	12"	18"	24"		-	Custom Len.	
$63.99	Call	$68.99	$70.99	$76.99		-	See Web	

MMCX PLUG RIGHT ANGLE TO SMA MALE RIGHT ANGLE



Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W07894					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.102" dia.	38 dB/100ft		84
12"	100CM	-	-	-	-	-	Custom Len.	
$90.99	$96.99	-	-	-	-	-	See Web	

MMCX PLUG RIGHT ANGLE TO SMA FEMALE



Standard Flexible Cable Assemblies

RG188-DS Coax, 50 Ohm

Part No. PE3W07068					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.118" dia.	30 dB/100ft	160 W	85
12"	24"	36"	48"	60"	50CM	Custom Len.		
$74.99	Call	Call	Call	Call	Call	See Web		

MMCX PLUG RIGHT ANGLE TO SMA FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39422					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22.5 dB/100ft	105 W	86
6"	9"	12"	18"	24"		-	Custom Len.	
$53.99	$49.99	$53.99	$60.99	$66.99		-	See Web	

MMBX PLUG TO MMBX PLUG



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4064				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	121.5 W	87
4"	6"	8"	12"	18"	24"	Custom Len.	
$61.99	$62.99	$64.99	$74.99	$72.99	$76.99	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4031				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	88
4"	6"	8"	12"	18"	24"	Custom Len.	
$56.99	$56.99	$56.99	$57.99	$57.99	$57.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3985				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	89
4"	6"	8"	12"	18"	24"	Custom Len.	
$55.99	$56.99	$56.99	$56.99	$57.99	$57.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4014				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	58 dB/100ft	160 W	90
4"	6"	8"	12"	18"	24"	Custom Len.	
$57.99	$57.99	$58.99	$59.99	$61.99	$62.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4048				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	91
4"	6"	8"	12"	18"	24"	Custom Len.	
$56.99	$57.99	$57.99	$59.99	$60.99	$61.99	See Web	

MMBX PLUG TO MMBX PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4032				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	92
4"	6"	8"	12"	18"	24"	Custom Len.	
$61.99	$61.99	$61.99	$61.99	$62.99	$62.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3986				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	93
4"	6"	8"	12"	18"	24"	Custom Len.	
$60.99	$60.99	$60.99	$60.99	$61.99	$61.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4015				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	58 dB/100ft	160 W	94
4"	6"	8"	12"	18"	24"	Custom Len.	
$61.99	$61.99	$62.99	$63.99	$65.99	$67.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4049				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	95
4"	6"	8"	12"	18"	24"	Custom Len.	
$60.99	$61.99	$61.99	$63.99	$64.99	$66.99	See Web	

MMBX PLUG TO N FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4040				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	96
4"	6"	8"	12"	18"	24"	Custom Len.	
$73.99	$73.99	$74.99	$74.99	$74.99	$74.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3993				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	97
4"	6"	8"	12"	18"	24"	Custom Len.	
$65.99	$65.99	$65.99	$66.99	$66.99	$67.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4023				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	58 dB/100ft	160 W	98
4"	6"	8"	12"	18"	24"	Custom Len.	
$74.99	$74.99	$75.99	$76.99	$78.99	$80.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4056				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	99
4"	6"	8"	12"	18"	24"	Custom Len.	
$74.99	$74.99	$75.99	$76.99	$78.99	$80.99	See Web	

MMBX PLUG TO SMA MALE



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4068				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	121.5 W	1
4"	6"	8"	12"	18"	24"	Custom Len.	
$60.99	$56.99	$58.99	$66.99	$65.99	$70.99	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4036				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	2
4"	6"	8"	12"	18"	24"	Custom Len.	
$53.99	$53.99	$53.99	$59.99	$53.99	$59.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3989				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	3
4"	6"	8"	12"	18"	24"	Custom Len.	
$61.99	$61.99	$61.99	$62.99	$62.99	$63.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4019				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	4
4"	6"	8"	12"	18"	24"	Custom Len.	
$53.99	$54.99	$55.99	$61.99	$57.99	$65.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C3854				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	5
4"	6"	8"	12"	18"	24"	Custom Len.	
$47.59	$48.19	$48.79	$49.99	$51.99	$53.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

MMBX PLUG TO SMA MALE RIGHT ANGLE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4044				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	6
4"	6"	8"	12"	18"	24"	Custom Len.	
$65.99	$65.99	$65.99	$65.99	$66.99	$66.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3997				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	7
4"	6"	8"	12"	18"	24"	Custom Len.	
$72.99	$72.99	$72.99	$72.99	$73.99	$74.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4027				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	8
4"	6"	8"	12"	18"	24"	Custom Len.	
$65.99	$66.99	$66.99	$68.99	$69.99	$71.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4060				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	9
4"	6"	8"	12"	18"	24"	Custom Len.	
$63.99	$63.99	$64.99	$65.99	$67.99	$69.99	See Web	

MMBX PLUG TO SMA FEMALE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4046				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	10
4"	6"	8"	12"	18"	24"	Custom Len.	
$64.99	$64.99	$64.99	$64.99	$65.99	$65.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3999				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	11
4"	6"	8"	12"	18"	24"	Custom Len.	
$71.99	$72.99	$72.99	$72.99	$73.99	$73.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4029				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	12
4"	6"	8"	12"	18"	24"	Custom Len.	
$64.99	$65.99	$66.99	$73.99	$68.99	$70.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4062				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	13
4"	6"	8"	12"	18"	24"	Custom Len.	
$63.99	$63.99	$64.99	$65.99	$67.99	$69.99	See Web	

MMBX PLUG TO SMA FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4066				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	121.5 W	14
4"	6"	8"	12"	18"	24"	Custom Len.	
$63.99	$59.99	$60.99	$70.99	$68.99	$73.99	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4034				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	15
4"	6"	8"	12"	18"	24"	Custom Len.	
$60.99	$60.99	$60.99	$65.99	$66.99	$61.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3922				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	16
4"	6"	8"	12"	18"	24"	Custom Len.	
$65.99	$65.99	$65.99	$65.99	$66.99	$66.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4017				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	58 dB/100ft	160 W	17
4"	6"	8"	12"	18"	24"	Custom Len.	
$60.99	$61.99	$61.99	$62.99	$64.99	$65.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4051				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	18
4"	6"	8"	12"	18"	24"	Custom Len.	
$67.99	$67.99	$68.99	$69.99	$71.99	$72.99	See Web	

MMBX PLUG TO REVERSE POLARITY SMA FEMALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4038				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	19
4"	6"	8"	12"	18"	24"	Custom Len.	
$71.99	$71.99	$71.99	$72.99	$72.99	$72.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3991				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	20
4"	6"	8"	12"	18"	24"	Custom Len.	
$51.99	$51.99	$52.99	$52.99	$53.99	$53.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4021				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	58 dB/100ft	160 W	21
4"	6"	8"	12"	18"	24"	Custom Len.	
$72.99	$72.99	$73.99	$74.99	$76.99	$77.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4054				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	22
4"	6"	8"	12"	18"	24"	Custom Len.	
$72.99	$72.99	$73.99	$74.99	$76.99	$77.99	See Web	

MMBX PLUG TO SSMB JACK BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W07532				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		23
12"	24"	36"	48"	60"	50CM	Custom Len.	
$86.99	$90.99	$94.99	$98.99	$103.99	$88.99	See Web	

MMBX PLUG TO TNC FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4042				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	24
4"	6"	8"	12"	18"	24"	Custom Len.	
$69.99	$69.99	$69.99	$70.99	$70.99	$70.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3995				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	25
4"	6"	8"	12"	18"	24"	Custom Len.	
$69.99	$65.99	$66.99	$70.99	$67.99	$67.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4025				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	26
4"	6"	8"	12"	18"	24"	Custom Len.	
$70.99	$70.99	$71.99	$79.99	$74.99	$75.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4058				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	27
4"	6"	8"	12"	18"	24"	Custom Len.	
$69.99	$69.99	$70.99	$71.99	$73.99	$74.99	See Web	

MMBX PLUG RIGHT ANGLE TO MMBX PLUG RIGHT ANGLE



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4065				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	121.5 W	28
4"	6"	8"	12"	18"	24"	Custom Len.	
$72.99	$74.99	$75.99	$78.99	$83.99	$87.99	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4033				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	29
4"	6"	8"	12"	18"	24"	Custom Len.	
$65.99	$65.99	$65.99	$66.99	$66.99	$66.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3987				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	30
4"	6"	8"	12"	18"	24"	Custom Len.	
$64.99	$64.99	$65.99	$65.99	$66.99	$66.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

RG316/U Coax, 50 Ohm

Part No. PE3C4016				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	31
4"	6"	8"	12"	18"	24"	Custom Len.	
$66.99	$66.99	$67.99	$75.99	$70.99	$71.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4050				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	32
4"	6"	8"	12"	18"	24"	Custom Len.	
$65.99	$66.99	$66.99	$67.99	$69.99	$71.99	See Web	

MMBX PLUG RIGHT ANGLE TO N FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4041				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	33
4"	6"	8"	12"	18"	24"	Custom Len.	
$78.99	$78.99	$78.99	$79.99	$79.99	$79.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3994				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	34
4"	6"	8"	12"	18"	24"	Custom Len.	
$70.99	$70.99	$70.99	$71.99	$71.99	$72.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4024				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	58 dB/100ft	160 W	35
4"	6"	8"	12"	18"	24"	Custom Len.	
$78.99	$79.99	$80.99	$81.99	$82.99	$84.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4057				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	36
4"	6"	8"	12"	18"	24"	Custom Len.	
$79.99	$79.99	$80.99	$81.99	$83.99	$84.99	See Web	

MMBX PLUG RIGHT ANGLE TO SMA MALE



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4069				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	121.5 W	37
4"	6"	8"	12"	18"	24"	Custom Len.	
$63.99	$59.99	$60.99	$69.99	$68.99	$72.99	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4037				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	38
4"	6"	8"	12"	18"	24"	Custom Len.	
$58.99	$58.99	$58.99	$62.99	$58.99	$59.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3990				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	39
4"	6"	8"	12"	18"	24"	Custom Len.	
$66.99	$66.99	$66.99	$66.99	$67.99	$68.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4020				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	40
4"	6"	8"	12"	18"	24"	Custom Len.	
$105.99	$105.99	$105.99	$113.99	$107.99	$117.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4053				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	41
4"	6"	8"	12"	18"	24"	Custom Len.	
$52.99	$52.99	$53.99	$59.99	$61.99	$58.99	See Web	

MMBX PLUG RIGHT ANGLE TO SMA MALE RIGHT ANGLE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4045				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	42
4"	6"	8"	12"	18"	24"	Custom Len.	
$70.99	$70.99	$70.99	$70.99	$70.99	$71.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3998				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	43
4"	6"	8"	12"	18"	24"	Custom Len.	
$76.99	$76.99	$77.99	$77.99	$78.99	$78.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4028				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	44
4"	6"	8"	12"	18"	24"	Custom Len.	
$70.99	$71.99	$71.99	$72.99	$74.99	$76.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4061				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	45
4"	6"	8"	12"	18"	24"	Custom Len.	
$68.99	$68.99	$69.99	$70.99	$72.99	$73.99	See Web	

MMBX PLUG RIGHT ANGLE TO SMA FEMALE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4047				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	46
4"	6"	8"	12"	18"	24"	Custom Len.	
$69.99	$69.99	$69.99	$69.99	$69.99	$70.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3W03154				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	47
4"	6"	8"	12"	18"	24"	Custom Len.	
$76.99	$76.99	$76.99	$77.99	$77.99	$78.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4030				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	48
4"	6"	8"	12"	18"	24"	Custom Len.	
$76.99	$77.99	$70.99	$79.99	$73.99	$75.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4063				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	49
4"	6"	8"	12"	18"	24"	Custom Len.	
$74.99	$68.99	$69.99	$77.99	$72.99	$73.99	See Web	

MMBX PLUG RIGHT ANGLE TO SMA FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4067				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	121.5 W	50
4"	6"	8"	12"	18"	24"	Custom Len.	
$66.99	$62.99	$63.99	$73.99	$71.99	$75.99	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4035				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	51
4"	6"	8"	12"	18"	24"	Custom Len.	
$64.99	$64.99	$64.99	$71.99	$71.99	$65.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C4807				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	52
12"	24"	36"	48"	60"	50CM	Custom Len.	
$88.99	$86.99	$87.99	$88.99	$89.99	$85.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4018				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	53
4"	6"	8"	12"	18"	24"	Custom Len.	
$71.99	$71.99	$71.99	$71.99	$72.99	$74.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4052				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	54
4"	6"	8"	12"	18"	24"	Custom Len.	
$71.99	$72.99	$72.99	$74.99	$75.99	$77.99	See Web	

MMBX PLUG RIGHT ANGLE TO REVERSE POLARITY SMA FEMALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4039				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	55
4"	6"	8"	12"	18"	24"	Custom Len.	
$76.99	$76.99	$76.99	$76.99	$77.99	$77.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3992				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	56
4"	6"	8"	12"	18"	24"	Custom Len.	
$61.99	$56.99	$56.99	$62.99	$57.99	$58.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

RG316/U Coax, 50 Ohm

Part No. PE3C4022				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	58 dB/100ft	160 W	57
4"	6"	8"	12"	18"	24"	Custom Len.	
$76.99	$77.99	$77.99	$79.99	$80.99	$82.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4055				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	58
4"	6"	8"	12"	18"	24"	Custom Len.	
$76.99	$77.99	$77.99	$79.99	$80.99	$82.99	See Web	

MMBX PLUG RIGHT ANGLE TO TNC FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4043				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	59
4"	6"	8"	12"	18"	24"	Custom Len.	
$74.99	$74.99	$74.99	$82.99	$82.99	$75.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3996				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	60
4"	6"	8"	12"	18"	24"	Custom Len.	
$77.99	$70.99	$70.99	$78.99	$71.99	$72.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4026				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	61
4"	6"	8"	12"	18"	24"	Custom Len.	
$74.99	$75.99	$76.99	$81.99	$83.99	$80.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4059				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	62
4"	6"	8"	12"	18"	24"	Custom Len.	
$73.99	$74.99	$74.99	$83.99	$85.99	$79.99	See Web	

N MALE TO 7/16 DIN MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE39143				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	63
12"	24"	36"	48"	60"	-	Custom Len.	
$159.99	$161.99	$161.99	$161.99	$163.99	-	See Web	

PE-C600 Coax, 50 Ohm

Part No. PE38436				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.7 dB/100ft	900 W	64
36"	48"	60"	72"	120"	-	Custom Len.	
$155.99	$161.99	$169.99	$173.99	$207.99	-	See Web	

LMR-400 Coax, 50 Ohm

Part No. PE3W03803				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		65
12"	24"	36"	48"	60"	50CM	Custom Len.	
$105.99	$107.99	$107.99	$109.99	$111.99	$105.99	See Web	

Low PIM Formable Cable Assemblies

PE-SR401FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2012				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.276" dia.			66
100CM	200CM	-	-	-	-	Custom Len.	
$193.99	$233.99	-	-	-	-	See Web	

PE-SR402FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2002				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.			67
100CM	200CM	300CM	-	-	-	Custom Len.	
Call	Call	Call	-	-	-	See Web	

Standard Formable Cable Assemblies

PE-SR401FL Coax, 50 Ohm

Part No. PE36178				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	68
12"	24"	36"	48"	60"	72"	Custom Len.	
$259.99	$277.99	$295.99	$313.99	$331.99	$349.99	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE35965				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	69
12"	24"	36"	48"	60"	72"	Custom Len.	
$229.99	$237.99	$247.99	$255.99	$263.99	$273.99	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE35284				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	70
12"	24"	36"	48"	60"	72"	Custom Len.	
$203.99	$207.99	$223.99	$213.99	$217.99	$221.99	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3207				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	71
12"	24"	36"	48"	60"	72"	Custom Len.	
$175.99	$175.99	$177.99	$177.99	$179.99	$179.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3216				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		72
12"	24"	36"	48"	60"	72"	Custom Len.	
$95.99	$103.99	$117.99	$117.99	$123.99	$129.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE34098				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	73
12"	24"	36"	48"	60"	72"	Custom Len.	
$197.99	$199.99	$201.99	$203.99	$205.99	$221.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3218				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	74
12"	24"	36"	48"	60"	72"	Custom Len.	
$203.99	$211.99	$231.99	$241.99	$249.99	$247.99	See Web	

RG217/U Coax, 50 Ohm

Part No. PE36170				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.	5.8 dB/100ft	260 W	75
12"	24"	36"	48"	60"	72"	Custom Len.	
$241.99	$245.99	$251.99	$257.99	$263.99	$267.99	See Web	

RG218/U Coax, 50 Ohm

Part No. PE36172				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.87" dia.	3.8 dB/100ft	560 W	76
12"	24"	36"	48"	60"	72"	Custom Len.	
$339.99	$353.99	$367.99	$407.99	$395.99	$409.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE33144				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	77
12"	24"	36"	48"	60"	72"	Custom Len.	
$92.99	$96.99	$99.99	$103.99	$107.99	$111.99	See Web	

RG393/U Coax, 50 Ohm

Part No. PE34357				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W	78
12"	24"	36"	48"	60"	72"	Custom Len.	
$215.99	$235.99	$253.99	$273.99	$311.99	$311.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34359				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	79
12"	24"	36"	48"	60"	72"	Custom Len.	
$105.99	$115.99	$121.99	$129.99	$139.99	$147.99	See Web	

PE-FF430 Coax, 50 Ohm

Part No. PE3C4000				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			80
60"	144"	-	-	-	-	Custom Len.	
$750.00	$980.00	-	-	-	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG402/U Coax, 50 Ohm

Part No. PE35963				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	81
12"	24"	36"	48"	60"	72"	Custom Len.	
$233.99	$241.99	$251.99	$259.99	$267.99	$277.99	See Web	

N MALE TO 7/16 DIN MALE RIGHT ANGLE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4136				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			82
12"	24"	36"	48"	60"	50CM	Custom Len.	
$141.99	$135.99	$141.99	$149.99	$155.99	$133.99	See Web	

N MALE TO 7/16 DIN FEMALE



Low PIM Formable Cable Assemblies

PE-SR401FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2014				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.276" dia.			83
100CM	200CM	-	-	-	-	Custom Len.	
Call	$219.99	-	-	-	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-SR402FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2005				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.			84
100CM	200CM	-	-	-	-	Custom Len.	
$151.99	Call	-	-	-	-	See Web	

Standard Flexible Cable Assemblies

PE-FF430 Coax, 50 Ohm

Part No. PE3C4001				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			85
60"	144"	-	-	-	-	Custom Len.	
$1,060.00	$1,320.00	-	-	-	-	See Web	

N MALE TO BNC MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE36065				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	86
12"	24"	36"	48"	60"	-	Custom Len.	
$46.99	$44.59	$48.99	$46.39	$51.99	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE35269				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	87
12"	24"	36"	48"	60"	-	Custom Len.	
$65.99	$67.99	$65.99	$70.99	$73.99	-	See Web	

LMR-240-UF Coax, 50 Ohm

Part No. PE3C2404				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft		88
12"	24"	36"	48"	60"	50CM	Custom Len.	
$47.39	$47.19	$48.79	$50.99	$52.99	$46.59	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3252				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	89
12"	24"	36"	48"	60"	72"	Custom Len.	
$82.99	$85.99	$95.99	$92.99	$103.99	$99.99	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3042				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	90
12"	24"	36"	48"	60"	72"	Custom Len.	
$50.99	$51.99	$52.99	$53.99	$54.99	$55.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3W00140				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	91
12"	24"	36"	48"	60"	50CM	Custom Len.	
$51.99	$58.99	$65.99	$72.99	$80.99	$56.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3378				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	92
6"	12"	18"	24"	36"	48"	Custom Len.	
$52.99	$52.99	$52.99	$58.99	$53.99	$60.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3C3379				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	93
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.99	$56.99	$59.99	$61.99	$64.99	$66.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3750				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	94
12"	24"	36"	48"	60"	72"	Custom Len.	
$91.99	$93.99	$95.99	$92.99	$94.99	$103.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3097				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	95
12"	24"	36"	48"	60"	72"	Custom Len.	
$97.99	$107.99	$117.99	$125.99	$127.99	$145.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3476				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	96
12"	24"	36"	48"	60"	72"	Custom Len.	
$49.99	$53.99	$57.99	$61.99	$65.99	$69.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C3380				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	97
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.99	$66.99	$70.99	$69.99	$73.99	$82.99	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3254				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	98
12"	24"	36"	48"	60"	72"	Custom Len.	
$101.99	$115.99	$133.99	$153.99	$171.99	$203.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3874				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	99
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.99	$76.99	$85.99	$94.99	$105.99	$113.99	See Web	

RG55B/U Coax, 53 Ohm

Part No. PE3477				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	1
12"	24"	36"	48"	60"	72"	Custom Len.	
$49.39	$52.99	$55.99	$62.99	$60.99	$63.99	See Web	

N MALE TO BNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE34882				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	2
12"	24"	36"	48"	60"	-	Custom Len.	
$81.99	$90.99	$99.99	$109.99	$119.99	-	See Web	

N MALE TO C FEMALE



Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE3W06365				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		3
12"	24"	36"	48"	60"	50CM	Custom Len.	
$137.99	$145.99	$153.99	$159.99	$167.99	$143.99	See Web	

N MALE TO GR874 SEXLESS



Standard Flexible Cable Assemblies

RG214/U Coax, 50 Ohm

Part No. PE3133				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	4
12"	24"	36"	48"	60"	72"	Custom Len.	
$165.99	$173.99	$183.99	$191.99	$201.99	$209.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3170				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	5
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.99	$74.99	$77.99	$81.99	$85.99	$88.99	See Web	

N MALE TO MCX PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

RG316-DS Coax, 50 Ohm

Part No. PE35276				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	26.1 dB/100ft	160 W	6
12"	24"	36"	48"	60"	50CM	Custom Len.	
$85.99	$89.99	$93.99	$97.99	$101.99	$83.99	See Web	

N MALE TO MINI UHF MALE



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3282				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	7
12"	24"	36"	48"	60"	72"	Custom Len.	
$50.99	$56.99	$57.99	$53.99	$59.99	$55.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3285				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		8
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.99	$60.99	$68.99	$76.99	$83.99	$91.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3280				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	9
12"	24"	36"	48"	60"	72"	Custom Len.	
$44.59	$48.19	$51.99	$55.99	$62.99	$62.99	See Web	

RG303/U Coax, 50 Ohm

Part No. PE3W04230				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.17" dia.	14 dB/100ft	650 W	10
12"	24"	36"	48"	60"	50CM	Custom Len.	
$45.19	$53.99	$62.99	$70.99	$79.99	$50.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

For our complete selection of cable assemblies, please visit our website

RG400/U Coax, 50 Ohm

Part No. PE3288				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	11
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.99	$68.99	$77.99	$85.99	$94.99	$103.99	See Web	

N MALE TO N MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE37940				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	12
36"	48"	60"	72"	120"	-	Custom Len.	
$41.79	$42.99	$43.99	$44.99	$49.19	-	See Web	

PE-C200 Coax, 50 Ohm

Part No. PE34693				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10.8 dB/100ft	170 W	13
12"	24"	36"	48"	60"	-	Custom Len.	
$59.99	$61.99	$65.99	$71.99	$76.99	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE37941				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	14
36"	48"	60"	72"	120"	-	Custom Len.	
$63.99	$65.99	$63.99	$68.99	$79.99	-	See Web	

PE-C300 Coax, 50 Ohm

Part No. PE36634				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	6.3 dB/100ft	350 W	15
12"	24"	36"	48"	60"	-	Custom Len.	
$87.99	$86.99	$96.99	$93.99	$97.99	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE34666				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	16
12"	24"	36"	48"	60"	-	Custom Len.	
$75.99	$80.99	$81.99	$83.99	$88.99	-	See Web	

Part No. PE37942				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	17
36"	48"	60"	72"	-	-	Custom Len.	
$84.99	$86.99	$82.99	$84.99	-	-	See Web	

PE-C600 Coax, 50 Ohm

Part No. PE37943				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.7 dB/100ft	900 W	18
36"	48"	60"	72"	120"	100CM	Custom Len.	
$133.99	$135.99	$139.99	$141.99	$163.99	$143.99	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3C0039				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		19
12"	24"	36"	48"	60"	-	Custom Len.	
$52.99	$53.99	$54.99	$56.99	$57.99	-	See Web	

Part No. PE3C0053				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		20
12"	24"	36"	48"	60"	-	Custom Len.	
$68.99	$69.99	$70.99	$71.99	$72.99	-	See Web	

Part No. PE3C0101				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		21
12"	24"	36"	48"	60"	240"	Custom Len.	
$58.99	$59.99	$60.99	$61.99	$62.99	Call	See Web	

LMR-400 Coax, 50 Ohm

Part No. PE3C0033				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		22
12"	24"	36"	48"	60"	-	Custom Len.	
$61.99	$62.99	$64.99	$66.99	$68.99	-	See Web	

Part No. PE3C0046				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		23
12"	24"	36"	48"	60"	-	Custom Len.	
$62.99	$64.99	$66.99	$67.99	$69.99	-	See Web	

Part No. PE3C0105				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		24
12"	24"	36"	48"	60"	-	Custom Len.	
$101.99	$103.99	$105.99	$107.99	$109.99	-	See Web	

LMR-600 Coax, 50 Ohm

Part No. PE3C0048				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft		25
12"	24"	36"	48"	60"	-	Custom Len.	
$177.99	$181.99	$175.99	$187.99	$181.99	-	See Web	

Part No. PE3C0062				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft		26
12"	24"	36"	48"	60"	-	Custom Len.	
$173.99	$175.99	$179.99	$183.99	$187.99	-	See Web	

Part No. PE3C0110				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft		27
12"	24"	36"	48"	60"	-	Custom Len.	
$141.99	$145.99	$139.99	$143.99	$155.99	-	See Web	

Part No. PE3C0112				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft		28
12"	24"	36"	48"	60"	-	Custom Len.	
$98.99	$96.99	$101.99	$103.99	$107.99	-	See Web	

LMR-195 Coax, 50 Ohm

Part No. PE3C0060				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		29
12"	24"	36"	48"	60"	-	Custom Len.	
$55.99	$56.99	$54.99	$55.99	$59.99	-	See Web	

Part No. PE3C0061				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		30
12"	24"	36"	48"	60"	-	Custom Len.	
$54.99	$55.99	$55.99	$53.99	$57.99	-	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE343				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		31
12"	24"	36"	48"	60"	50CM	Custom Len.	
$153.99	$175.99	$195.99	$215.99	$237.99	$167.99	See Web	

Part No. PE3C0231				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.32" dia.	7.2 dB/100ft		32
36"	48"	60"	72"	120"	2220"	Custom Len.	
$525.00	$540.00	$580.00	$605.00	$920.00	Call	See Web	

PE-SF200LL Coax, 50 Ohm

Part No. PE3TC1102				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.185" dia.			33
24"	36"	48"	72"	100CM	200CM	Custom Len.	
$101.99	$115.99	$127.99	Call	Call	Call	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5255				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			34
12"	24"	36"	48"	60"	50CM	Custom Len.	
$263.99	$289.99	$315.99	$341.99	$367.99	$279.99	See Web	

Precision Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39465				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	35
6"	9"	12"	18"	24"	-	Custom Len.	
$65.99	$68.99	$65.99	$70.99	$80.99	-	See Web	

PE-80TEST Coax, 50 Ohm

Part No. PE3TC0103				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			36
24"	48"	72"	200CM	-	400CM	Custom Len.	
$427.99	$535.00	$645.00	Call	-	Call	See Web	

PE-90TEST Coax, 50 Ohm

Part No. PE3TC0302				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.151" dia.			37
24"	48"	72"	-	-	-	Custom Len.	
$353.99	$453.99	$555.00	-	-	-	See Web	

Low PIM Formable Cable Assemblies

PE-SR401FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2011				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.276" dia.			38
100CM	200CM	401CM	-	-	-	Custom Len.	
$137.99	$177.99	Call	-	-	-	See Web	

PE-SR402FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2000				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.			39
76CM	100CM	150CM	200CM	-	-	Custom Len.	
Call	$101.99	Call	$117.99	-	-	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7842				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		40
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.99	$72.99	$77.99	$82.99	$86.99	$71.99	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6202				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	41
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.99	$72.99	$79.99	$86.99	$93.99	$69.99	See Web	

Test Flexible Cable Assemblies

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA1803				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			42
24"	36"	48"	60"	-	-	Custom Len.	
$1,000.00	$1,160.00	$1,120.00	$1,290.00	-	-	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE330				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	4.6 dB/100ft		43
12"	24"	36"	48"	60"	50CM	Custom Len.	
$345.99	$377.99	$411.99	$443.99	$477.99	$365.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For Custom Lengths, Metric Lengths or Special Configurations, Please call (949) 261-1920

For our complete selection of cable assemblies, please visit our website

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34146				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	44
6"	12"	18"	24"	36"	48"	Custom Len.	
$109.99	$115.99	$119.99	$121.99	$129.99	$139.99	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34149				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	45
6"	12"	18"	24"	36"	48"	Custom Len.	
$161.99	$171.99	$169.99	$189.99	$209.99	$231.99	See Web	

Part No. PE3W00109				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						1,400 W	46
12"	24"	36"	48"	60"	50CM	Custom Len.	
$119.99	$141.99	$161.99	$181.99	$201.99	$133.99	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE3472				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	47
6"	12"	18"	24"	36"	48"	Custom Len.	
$103.99	$107.99	$111.99	$117.99	$119.99	$127.99	See Web	

Part No. PE39451				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	400 W	48
6"	9"	12"	18"	24"	-	Custom Len.	
$76.99	Call	$65.99	$69.99	$74.99	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE39443				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	49
6"	9"	12"	18"	24"	-	Custom Len.	
$68.99	Call	Call	$86.99	$78.99	-	See Web	

Part No. PE3963				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	50
6"	12"	18"	24"	36"	48"	Custom Len.	
$135.99	$135.99	$141.99	$147.99	$161.99	$173.99	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39457				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	51
6"	9"	12"	18"	24"	-	Custom Len.	
$55.99	Call	$45.19	Call	Call	-	See Web	

Standard Flexible Cable Assemblies

PE-B400 Coax, 50 Ohm

Part No. PE3629				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.403" dia.	6 dB/100ft	190 W	52
12"	24"	36"	48"	60"	-	Custom Len.	
$66.99	$68.99	$70.99	$72.99	$74.99	-	See Web	

PE-C500 Coax, 50 Ohm

Part No. PE35522				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.5" dia.	3.5 dB/100ft	720 W	53
12"	24"	36"	48"	60"	-	Custom Len.	
$115.99	$121.99	$125.99	$129.99	$133.99	-	See Web	

PE-P141 Coax, 50 Ohm

Part No. PE302				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			54
12"	24"	36"	48"	60"	72"	Custom Len.	
$209.99	$223.99	$237.99	$251.99	$267.99	$293.99	See Web	

Part No. PE352				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.	11.2 dB/100ft	600 W	55
12"	24"	36"	48"	60"	72"	Custom Len.	
$153.99	$167.99	$181.99	$195.99	$209.99	$211.99	See Web	

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1047				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			56
12"	24"	27"	28"	36"	50CM	Custom Len.	
$113.99	$131.99	Call	Call	$153.99	$125.99	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE33377				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	57
12"	24"	36"	48"	60"	-	Custom Len.	
$68.99	$80.99	$92.99	$105.99	$117.99	-	See Web	

PE-FF430 Coax, 50 Ohm

Part No. PE3C4002				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			58
60"	144"	-	-	-	-	Custom Len.	
$615.00	$900.00	-	-	-	-	See Web	

Part No. PE3C4005				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			59
60"	100CM	-	-	-	-	Custom Len.	
Call	$745.00	-	-	-	-	See Web	

LMR-400-UF Coax, 50 Ohm

Part No. PE3C0218				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	5 dB/100ft		60
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.99	$65.99	$68.99	$71.99	$74.99	$64.99	See Web	

Part No. PE3W08067				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	5 dB/100ft		61
12"	60"	-	-	-	-	Custom Len.	
$63.99	$74.99	-	-	-	-	See Web	

LMR-195 Coax, 50 Ohm

Part No. PE3C0118				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		62
12"	24"	36"	48"	60"	-	Custom Len.	
$60.99	$61.99	$58.99	$62.99	$63.99	-	See Web	

LMR-600-UF Coax, 50 Ohm

Part No. PE3C7615				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	3.17 dB/100ft		63
12"	24"	36"	48"	60"	50CM	Custom Len.	
$85.99	$89.99	$94.99	$98.99	$103.99	$83.99	See Web	

RG8A/U Coax, 50 Ohm

Part No. PE3570				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	64
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.99	$86.99	$90.99	$94.99	$98.99	$103.99	See Web	

RG8X Coax, 50 Ohm

Part No. PE33720				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13.5 dB/100ft	60 W	65
12"	24"	36"	48"	60"	-	Custom Len.	
$91.99	$90.99	$94.99	$105.99	$103.99	-	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3441				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	66
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.99	$60.99	$60.99	$61.99	$62.99	$63.99	See Web	

RG141A/U Coax, 50 Ohm

Part No. PE36589				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W	67
12"	24"	36"	48"	60"	-	Custom Len.	
$75.99	$89.99	$97.99	$107.99	$115.99	-	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3455				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	68
6"	12"	18"	24"	30"	36"	Custom Len.	
$58.99	$62.99	$65.99	$69.99	$70.99	$77.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE36273				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	69
12"	24"	36"	48"	60"	-	Custom Len.	
$64.99	$69.99	$65.99	$71.99	$72.99	-	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE33527				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	70
12"	24"	36"	48"	60"	72"	Custom Len.	
$94.99	$95.99	$91.99	$92.99	$93.99	$95.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE33525				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	71
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.99	$73.99	$76.99	$78.99	$81.99	$84.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3496				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	72
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.99	$80.99	$82.99	$84.99	$86.99	$89.99	See Web	

RG217/U Coax, 50 Ohm

Part No. PE3997				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.	5.8 dB/100ft	260 W	73
12"	24"	36"	48"	60"	72"	Custom Len.	
$121.99	$127.99	$133.99	$139.99	$145.99	$141.99	See Web	

RG218/U Coax, 50 Ohm

Part No. PE33236				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.87" dia.	5 dB/100ft	600 W	74
24"	48"	60"	72"	84"	96"	Custom Len.	
$321.99	$351.99	$345.99	$383.99	$373.99	$389.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3447				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	75
6"	12"	16"	18"	24"	30"	Custom Len.	
$57.99	$59.99	Call	$61.99	$62.99	$62.99	See Web	

Part No. PE3W00417				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	76
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$74.99	$78.99	$82.99	$86.99	$73.99	See Web	

RG225/U Coax, 50 Ohm

Part No. PE33269				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	77
12"	24"	36"	48"	60"	-	Custom Len.	
$109.99	$149.99	$201.99	$231.99	$273.99	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

For our complete selection of cable assemblies, please visit our website

RG316/U Coax, 50 Ohm

Part No. PE3487				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	78
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.99	$81.99	$78.99	$82.99	$93.99	$89.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE33288				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	79
12"	24"	36"	48"	60"	-	Custom Len.	
$65.99	$69.99	$72.99	$76.99	$80.99	-	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3607				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	80
12"	24"	36"	48"	60"	72"	Custom Len.	
$99.99	$121.99	$139.99	$159.99	$181.99	$201.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3653				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	81
12"	24"	36"	48"	60"	72"	Custom Len.	
$74.99	$83.99	$92.99	$103.99	$111.99	$121.99	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE34142				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	40 dB/100ft	32 W	82
6"	12"	18"	24"	36"	48"	Custom Len.	
$111.99	$123.99	$123.99	$137.99	$141.99	$153.99	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE34144				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	83
6"	12"	18"	24"	36"	48"	Custom Len.	
$111.99	$117.99	$121.99	$125.99	$135.99	$147.99	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34138				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					13 dB/100ft	450 W	84
6"	12"	18"	24"	36"	48"	Custom Len.	
$97.99	$103.99	$109.99	$109.99	$119.99	$129.99	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34140				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	85
6"	12"	18"	24"	36"	48"	Custom Len.	
$119.99	$125.99	$129.99	$135.99	$145.99	$155.99	See Web	

RG401/U Coax, 50 Ohm

Part No. PE3782				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	1,400 W	86
6"	12"	18"	24"	36"	48"	Custom Len.	
$171.99	$171.99	$185.99	$199.99	$225.99	$267.99	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3827				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	87
6"	12"	18"	24"	36"	48"	Custom Len.	
$103.99	$103.99	$113.99	$119.99	$121.99	$127.99	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3920				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	88
6"	12"	18"	24"	36"	48"	Custom Len.	
$121.99	$125.99	$129.99	$133.99	$151.99	$149.99	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE3995				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	661 W	89
6"	12"	18"	24"	36"	48"	Custom Len.	
$163.99	$173.99	$175.99	$185.99	$207.99	$229.99	See Web	

Standard Flexible Cable Assemblies

RG11A/U Coax, 75 Ohm

Part No. PE33479				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W	90
12"	24"	36"	48"	60"	-	Custom Len.	
$82.99	$85.99	$82.99	$84.99	$86.99	-	See Web	

RG55B/U Coax, 53 Ohm

Part No. PE3499				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	91
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.99	$62.99	$65.99	$68.99	$71.99	$73.99	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE36181				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	92
12"	24"	36"	48"	60"	-	Custom Len.	
$48.79	$50.99	$51.99	$53.99	$54.99	-	See Web	

N MALE TO N MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4139				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	93
12"	24"	36"	48"	60"	50CM	Custom Len.	
$113.99	$119.99	$125.99	$131.99	$139.99	$117.99	See Web	

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38934				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		94
12"	24"	36"	48"	60"	-	Custom Len.	
$69.99	$70.99	$72.99	$74.99	$75.99	-	See Web	

PE-C195 Coax, 50 Ohm

Part No. PE37944				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	95
36"	48"	60"	72"	120"	-	Custom Len.	
$64.99	$65.99	$66.99	$67.99	$71.99	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE37945				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	96
36"	48"	60"	72"	120"	-	Custom Len.	
$78.99	$79.99	$80.99	$84.99	$97.99	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE37946				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	97
36"	48"	60"	72"	120"	-	Custom Len.	
$111.99	$113.99	$115.99	$119.99	$125.99	-	See Web	

PE-C600 Coax, 50 Ohm

Part No. PE37947				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.7 dB/100ft	900 W	98
36"	48"	60"	72"	120"	-	Custom Len.	
$157.99	$161.99	$173.99	$167.99	$179.99	-	See Web	

LMR-400 Coax, 50 Ohm

Part No. PE3C0041				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		99
12"	24"	36"	48"	60"	-	Custom Len.	
$98.99	$94.99	$96.99	$103.99	$105.99	-	See Web	
Part No. PE3C0106				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		1
12"	24"	36"	48"	60"	-	Custom Len.	
$98.99	$101.99	$99.99	$101.99	$105.99	-	See Web	
Part No. PE3W00430				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		2
12"	24"	36"	48"	60"	50CM	Custom Len.	
$94.99	$96.99	$98.99	$99.99	$101.99	$95.99	See Web	

LMR-400-DB Coax, 50 Ohm

Part No. PE3W01127				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.15 dB/100ft		3
12"	24"	36"	48"	60"	50CM	Custom Len.	
$89.99	$91.99	$93.99	$95.99	$96.99	$90.99	See Web	

LMR-600 Coax, 50 Ohm

Part No. PE3C0050				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft		4
12"	24"	36"	48"	60"	-	Custom Len.	
$141.99	$143.99	$139.99	$143.99	$147.99	-	See Web	
Part No. PE3C0111				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft		5
12"	24"	36"	48"	60"	-	Custom Len.	
$129.99	$125.99	$135.99	$131.99	$143.99	-	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5285				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			6
12"	24"	36"	48"	60"	50CM	Custom Len.	
$337.99	$363.99	$389.99	$417.99	$443.99	$353.99	See Web	

LMR-600-DB Coax, 50 Ohm

Part No. PE3W08467				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft		7
48"	50CM	100CM	-	-	-	Custom Len.	
$191.99	$183.99	$187.99	-	-	-	See Web	

Precision Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39453				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	8
6"	9"	12"	18"	24"	-	Custom Len.	
$71.99	$74.99	$70.99	$103.99	$109.99	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE39445				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	9
6"	9"	12"	18"	24"	-	Custom Len.	
$64.99	$67.99	Call	Call	Call	-	See Web	

Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

For Custom Lengths, Metric Lengths or Special Configurations, Please call (949) 261-1920

For our complete selection of cable assemblies, please visit our website

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39459				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	10
6"	9"	12"	18"	24"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7967				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			11
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$65.99	$69.99	$74.99	$78.99	$59.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C7999				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			12
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$59.99	$62.99	$64.99	$67.99	$57.99	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7843				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		13
12"	50CM	24"	36"	48"	60"	Custom Len.	
$72.99	$75.99	$76.99	$80.99	$85.99	$89.99	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6205				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	14
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.99	$73.99	$79.99	$86.99	$93.99	$70.99	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C6346				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			15
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$61.99	$64.99	$66.99	$69.99	$60.99	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C6361				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			16
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$63.99	$66.99	$70.99	$73.99	$62.99	See Web	

SPO-500 Coax, 50 Ohm

Part No. PE3C6372				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.53" dia.			17
12"	24"	36"	48"	60"	50CM	Custom Len.	
$49.59	$52.99	$56.99	$59.99	$62.99	$51.99	See Web	

SPF-500 Coax, 50 Ohm

Part No. PE3C6375				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.			18
12"	24"	36"	48"	60"	50CM	Custom Len.	
$50.99	$55.99	$60.99	$64.99	$69.99	$54.99	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3240				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		19
12"	24"	36"	48"	60"	50CM	Custom Len.	
$321.99	$353.99	$387.99	$419.99	$453.99	$341.99	See Web	

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39467				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	20
6"	9"	12"	18"	24"	-	Custom Len.	
$101.99	$105.99	$101.99	$113.99	Call	-	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3699				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	21
12"	24"	36"	48"	60"	72"	Custom Len.	
$103.99	$111.99	$115.99	$119.99	$117.99	$121.99	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3143				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	22
12"	24"	36"	48"	60"	72"	Custom Len.	
$82.99	$83.99	$77.99	$78.99	$79.99	$80.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3726				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	23
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.99	$88.99	$96.99	$105.99	$111.99	$113.99	See Web	
Part No. PE3W06863				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			24
12"	24"	36"	48"	60"	50CM	Custom Len.	
$71.99	$79.99	$86.99	$93.99	$101.99	$76.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE34205				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	25
12"	24"	36"	48"	60"	72"	Custom Len.	
$80.99	$81.99	$82.99	$82.99	$83.99	$83.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34212				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	26
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.99	$80.99	$83.99	$85.99	$88.99	$91.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3797				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	27
12"	24"	36"	48"	60"	72"	Custom Len.	
$101.99	$111.99	$113.99	$115.99	$109.99	$119.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3071				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	28
12"	24"	36"	48"	60"	72"	Custom Len.	
$121.99	$129.99	$139.99	$141.99	$159.99	$167.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3168				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	29
12"	24"	36"	48"	60"	72"	Custom Len.	
$83.99	$81.99	$91.99	$95.99	$91.99	$103.99	See Web	

RG225/U Coax, 50 Ohm

Part No. PE34203				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	30
12"	24"	36"	48"	60"	72"	Custom Len.	
$143.99	$183.99	$223.99	$263.99	$303.99	$343.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34210				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	31
12"	24"	36"	48"	60"	72"	Custom Len.	
$83.99	$87.99	$96.99	$94.99	$97.99	$109.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34207				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	32
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.99	$81.99	$85.99	$88.99	$92.99	$96.99	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3255				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	33
12"	24"	36"	48"	60"	72"	Custom Len.	
$121.99	$147.99	$167.99	$189.99	$209.99	$229.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE33321				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	34
12"	24"	36"	48"	60"	72"	Custom Len.	
$89.99	$103.99	$113.99	$121.99	$123.99	$139.99	See Web	

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1048				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			35
12"	24"	36"	50CM	100CM	-	Custom Len.	
$109.99	$123.99	$143.99	$117.99	$149.99	-	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE345				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft	820 W	36
12"	24"	36"	48"	60"	50CM	Custom Len.	
$285.99	$305.99	$325.99	$347.99	$367.99	$297.99	See Web	

PE-1/2 Helical Coax, 50 Ohm

Part No. PE37970				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.54" dia.			37
36"	72"	-	-	-	-	Custom Len.	
Call	Call	-	-	-	-	See Web	

PE-FF430 Coax, 50 Ohm

Part No. PE3C4003				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			38
60"	144"	-	-	-	-	Custom Len.	
$875.00	$1,290.00	-	-	-	-	See Web	
Part No. PE3C4006				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			39
60"	100CM	-	-	-	-	Custom Len.	
Call	$990.00	-	-	-	-	See Web	

LMR-400-UF Coax, 50 Ohm

Part No. PE3C3643				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	5 dB/100ft		40
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.99	$68.99	$71.99	$74.99	$77.99	$66.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

N MALE TO N FEMALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE37948				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	41
36"	48"	60"	72"	120"	-	Custom Len.	
$42.59	$41.19	$41.99	$42.99	$46.59	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE37949				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	42
36"	48"	60"	72"	120"	-	Custom Len.	
$61.99	$62.99	$63.99	$64.99	$69.99	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE34716				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	43
12"	24"	36"	48"	60"	-	Custom Len.	
$85.99	$86.99	$88.99	$90.99	$98.99	-	See Web	

Part No. PE37950				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	44
36"	48"	60"	72"	120"	-	Custom Len.	
$89.99	$90.99	$92.99	$94.99	$101.99	-	See Web	

PE-C600 Coax, 50 Ohm

Part No. PE37951				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.7 dB/100ft	900 W	45
36"	48"	72"	120"	300CM	-	Custom Len.	
$139.99	$143.99	$157.99	$161.99	$167.99	-	See Web	

PE-SF200LL Coax, 50 Ohm

Part No. PE3TC1103				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.185" dia.			46
24"	36"	48"	72"	100CM	200CM	Custom Len.	
$98.99	$113.99	$125.99	Call	Call	$163.99	See Web	

LMR-400 Coax, 50 Ohm

Part No. PE3W00676				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.			47
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.99	$73.99	$75.99	$77.99	$78.99	$73.99	See Web	

Precision Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39454				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	48
6"	9"	12"	18"	24"	-	Custom Len.	
$98.99	Call	Call	Call	Call	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE39446				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	49
6"	9"	12"	18"	24"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

PE-80TEST Coax, 50 Ohm

Part No. PE3TC0104				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			50
24"	48"	72"	-	-	-	Custom Len.	
$481.99	$590.00	$700.00	-	-	-	See Web	

Low PIM Formable Cable Assemblies

PE-SR402FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2001				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.			51
200CM	-	-	-	-	-	Custom Len.	
Call	-	-	-	-	-	See Web	

Low PIM Flexible Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4138				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	52
12"	24"	36"	48"	60"	50CM	Custom Len.	
$109.99	$117.99	$121.99	$129.99	$135.99	$113.99	See Web	

TFT-402 Coax, 50 Ohm

Part No. PE3C7969				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			53
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$62.99	$66.99	$71.99	$75.99	$56.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8001				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			54
12"	24"	36"	48"	60"	50CM	Custom Len.	
$53.99	$56.99	$58.99	$60.99	$62.99	$52.99	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7844				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		55
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.99	$73.99	$77.99	$82.99	$86.99	$71.99	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6200				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	56
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.99	$70.99	$77.99	$83.99	$90.99	$67.99	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C8491				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			57
7"	18CM	-	-	-	-	Custom Len.	
$51.99	$54.99	$57.99	$61.99	$64.99	$53.99	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C8508				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			58
7"	18CM	-	-	-	-	Custom Len.	
$50.99	$53.99	$55.99	$58.99	$60.99	$52.99	See Web	

Test Flexible Cable Assemblies

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA1804				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			59
24"	48"	-	-	-	-	Custom Len.	
$1,030.00	$1,140.00	-	-	-	-	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE331				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	4.6 dB/100ft		60
12"	24"	36"	48"	60"	50CM	Custom Len.	
$505.00	$535.00	$540.00	$575.00	$610.00	$495.99	See Web	

Part No. PE3C3241				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		61
12"	24"	36"	48"	60"	50CM	Custom Len.	
$297.99	$329.99	$361.99	$393.99	$425.99	$317.99	See Web	

Standard Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C0125				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		62
12"	24"	36"	48"	60"	-	Custom Len.	
$153.99	$157.99	$159.99	$163.99	$167.99	-	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34291				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	63
6"	12"	18"	24"	36"	48"	Custom Len.	
$119.99	$121.99	$125.99	$131.99	$139.99	$147.99	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34293				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	64
6"	12"	18"	24"	36"	48"	Custom Len.	
$121.99	$129.99	$139.99	$149.99	$167.99	$185.99	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE3485				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	65
6"	12"	18"	24"	36"	48"	Custom Len.	
$103.99	$107.99	$111.99	$121.99	$123.99	$133.99	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3965				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	66
6"	12"	18"	24"	36"	48"	Custom Len.	
$113.99	$121.99	$125.99	$131.99	$143.99	$155.99	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3714				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	67
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.99	$69.99	$70.99	$65.99	$66.99	$67.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3996				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	68
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.99	$75.99	$82.99	$90.99	$98.99	$105.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34283				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	69
12"	24"	36"	48"	60"	72"	Custom Len.	
$75.99	$78.99	$81.99	$84.99	$87.99	$89.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

RG213/U Coax, 50 Ohm

Part No. PE3232				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	9 dB/100ft	190 W	70
12"	24"	36"	48"	60"	72"	Custom Len.	
$81.99	$83.99	$85.99	$88.99	$90.99	$92.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3650				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	71
12"	24"	36"	48"	60"	72"	Custom Len.	
$88.99	$98.99	$109.99	$119.99	$121.99	$135.99	See Web	

RG217/U Coax, 50 Ohm

Part No. PE34274				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.	5.8 dB/100ft	260 W	72
12"	24"	36"	48"	60"	72"	Custom Len.	
$157.99	$163.99	$167.99	$173.99	$179.99	$183.99	See Web	

RG218/U Coax, 50 Ohm

Part No. PE34276				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.87" dia.	3.8 dB/100ft	560 W	73
12"	24"	36"	48"	60"	72"	Custom Len.	
$239.99	$253.99	$267.99	$281.99	$293.99	$329.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3667				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	74
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.99	$61.99	$65.99	$73.99	$77.99	$81.99	See Web	

RG225/U Coax, 50 Ohm

Part No. PE33728				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	75
12"	24"	36"	48"	60"	72"	Custom Len.	
$109.99	$149.99	$189.99	$229.99	$269.99	$309.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3986				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	76
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.99	$85.99	$84.99	$87.99	$91.99	$95.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34281				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	26.1 dB/100ft	160 W	77
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.99	$74.99	$77.99	$81.99	$85.99	$88.99	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3977				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W	78
12"	24"	36"	48"	60"	72"	Custom Len.	
$99.99	$121.99	$139.99	$159.99	$169.99	$187.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3617				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	79
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.99	$87.99	$96.99	$107.99	$115.99	$117.99	See Web	

Part No. PE3W07899				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	80
18"	24"	48"	50CM	100CM	150CM	Custom Len.	
$77.99	$82.99	$101.99	$79.99	$94.99	$109.99	See Web	

PE-1/2 Helical Coax, 50 Ohm

Part No. PE37969				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.54" dia.			81
36"	72"	-	-	-	-	Custom Len.	
Call	Call	-	-	-	-	See Web	

PE-FF430 Coax, 50 Ohm

Part No. PE3C4004				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			82
60"	144"	-	-	-	-	Custom Len.	
$610.00	$900.00	-	-	-	-	See Web	

Part No. PE3C4007				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			83
60"	100CM	-	-	-	-	Custom Len.	
Call	$800.00	-	-	-	-	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE34287				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	84
6"	12"	18"	24"	36"	48"	Custom Len.	
$119.99	$125.99	$131.99	$137.99	$149.99	$161.99	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE34296				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	85
6"	12"	18"	24"	36"	48"	Custom Len.	
$119.99	$123.99	$129.99	$135.99	$145.99	$155.99	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE3988				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	86
6"	12"	18"	24"	36"	48"	Custom Len.	
$123.99	$133.99	$143.99	$155.99	$175.99	$197.99	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34289				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	87
6"	12"	18"	24"	36"	48"	Custom Len.	
$103.99	$109.99	$115.99	$119.99	$129.99	$141.99	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34285				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	88
6"	12"	18"	24"	36"	48"	Custom Len.	
$113.99	$117.99	$121.99	$127.99	$137.99	$147.99	See Web	

RG401/U Coax, 50 Ohm

Part No. PE3979				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	89
6"	12"	18"	24"	36"	48"	Custom Len.	
$127.99	$141.99	$153.99	$167.99	$211.99	$219.99	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3829				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	90
6"	12"	18"	24"	36"	48"	Custom Len.	
$115.99	$115.99	$121.99	$123.99	$133.99	$141.99	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3921				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	91
6"	12"	18"	24"	36"	48"	Custom Len.	
$111.99	$115.99	$119.99	$121.99	$129.99	$137.99	See Web	

N MALE TO
N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Low Loss Flexible Cable Assemblies

PE-C240 Coax, 50 Ohm

Part No. PE38672				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	92
36"	48"	60"	72"	120"	-	Custom Len.	
$67.99	$65.99	$67.99	$72.99	$85.99	-	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE344				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		93
12"	24"	36"	48"	60"	50CM	Custom Len.	
$233.99	$253.99	$275.99	$295.99	$317.99	$247.99	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5257				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			94
12"	24"	36"	48"	60"	50CM	Custom Len.	
$295.99	$323.99	$349.99	$375.99	$401.99	$313.99	See Web	

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7970				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			95
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$63.99	$67.99	$72.99	$76.99	$57.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8002				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			96
12"	24"	36"	48"	60"	50CM	Custom Len.	
$55.99	$57.99	$59.99	$61.99	$64.99	$54.99	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7845				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		97
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.99	$73.99	$77.99	$82.99	$86.99	$71.99	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6201				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	98
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.99	$70.99	$77.99	$83.99	$90.99	$67.99	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C8492				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			99
7"	18CM	-	-	-	-	Custom Len.	
$51.99	$54.99	$57.99	$61.99	$64.99	$53.99	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C8509				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			1
7"	18CM	-	-	-	-	Custom Len.	
$50.99	$53.99	$55.99	$58.99	$60.99	$52.99	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34156				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	2
6"	12"	18"	24"	36"	48"	Custom Len.	
$119.99	$123.99	$129.99	$133.99	$141.99	$149.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

For our complete selection of cable assemblies, please visit our website

PE-SR401FL Coax, 50 Ohm

Part No. PE34150				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	3
6"	12"	18"	24"	36"	48"	Custom Len.	
$123.99	$131.99	$141.99	$149.99	$167.99	$185.99	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE3488				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	4
6"	12"	18"	24"	36"	48"	Custom Len.	
$113.99	$113.99	$117.99	$119.99	$129.99	$137.99	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3971				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	5
6"	12"	18"	24"	36"	48"	Custom Len.	
$119.99	$125.99	$131.99	$137.99	$151.99	$163.99	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3966				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	6
12"	24"	36"	48"	60"	72"	Custom Len.	
$101.99	$98.99	$103.99	$105.99	$109.99	$113.99	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3320				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	7
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.99	$70.99	$67.99	$72.99	$68.99	$69.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3034				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		8
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.99	$78.99	$85.99	$93.99	$101.99	$109.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE34201				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	9
12"	24"	36"	48"	60"	72"	Custom Len.	
$86.99	$88.99	$89.99	$90.99	$91.99	$92.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34181				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	10
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.99	$81.99	$83.99	$86.99	$89.99	$91.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE33543				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	11
12"	24"	36"	48"	60"	72"	Custom Len.	
$91.99	$93.99	$95.99	$97.99	$99.99	$103.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3217				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	12
12"	24"	36"	48"	60"	72"	Custom Len.	
$86.99	$95.99	$105.99	$115.99	$123.99	$133.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3686				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	13
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.99	$68.99	$71.99	$81.99	$78.99	$89.99	See Web	

RG225/U Coax, 50 Ohm

Part No. PE34194				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	14
12"	24"	36"	48"	60"	72"	Custom Len.	
$109.99	$147.99	$187.99	$227.99	$267.99	$307.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE33534				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	15
12"	24"	36"	48"	60"	72"	Custom Len.	
$84.99	$88.99	$91.99	$95.99	$105.99	$103.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34198				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	26.1 dB/100ft	160 W	16
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.99	$82.99	$86.99	$89.99	$93.99	$96.99	See Web	

RG393/U Coax, 50 Ohm

Part No. PE33530				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	17
12"	24"	36"	48"	60"	72"	Custom Len.	
$90.99	$111.99	$127.99	$147.99	$165.99	$185.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3227				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	18
12"	24"	36"	48"	60"	72"	Custom Len.	
$84.99	$93.99	$95.99	$113.99	$113.99	$129.99	See Web	

PE-P141 Coax, 50 Ohm

Part No. PE3C3255				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.	11.2 dB/100ft	550 W	19
12"	24"	36"	48"	60"	50CM	Custom Len.	
$103.99	$117.99	$129.99	$143.99	$157.99	$113.99	See Web	

LMR-400-UF Coax, 50 Ohm

Part No. PE3W02547				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	5 dB/100ft		20
12"	24"	36"	48"	60"	50CM	Custom Len.	
$67.99	$81.99	$85.99	$88.99	$91.99	$80.99	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE34152				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	21
6"	12"	18"	24"	36"	48"	Custom Len.	
$121.99	$127.99	$133.99	$139.99	$151.99	$163.99	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE34154				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	22
6"	12"	18"	24"	36"	48"	Custom Len.	
$121.99	$125.99	$131.99	$137.99	$147.99	$157.99	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34158				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	23
6"	12"	18"	24"	36"	48"	Custom Len.	
$115.99	$115.99	$119.99	$125.99	$135.99	$147.99	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34161				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	24
6"	12"	18"	24"	36"	48"	Custom Len.	
$119.99	$123.99	$127.99	$133.99	$143.99	$153.99	See Web	

RG401/U Coax, 50 Ohm

Part No. PE3983				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	25
6"	12"	18"	24"	36"	48"	Custom Len.	
$151.99	$151.99	$165.99	$177.99	$205.99	$231.99	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3830				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	26
6"	12"	18"	24"	36"	48"	Custom Len.	
$105.99	$105.99	$111.99	$121.99	$123.99	$131.99	See Web	

Part No. PE3C3286				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	27
12"	50CM	24"	36"	100CM	48"	Custom Len.	
$92.99	$93.99	$97.99	$107.99	$109.99	$117.99	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE3993				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	28
6"	12"	18"	24"	36"	48"	Custom Len.	
$125.99	$135.99	$145.99	$157.99	$177.99	$199.99	See Web	

N MALE TO
N FEMALE 4 HOLE FLANGE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3W02012				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		29
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$60.99	$61.99	$62.99	$62.99	$60.99	See Web	

N MALE TO
NMO MOUNT SEXLESS



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37850				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	30
60"	120"	180"	-	-	-	Custom Len.	
$64.99	$69.99	$74.99	-	-	-	See Web	

N MALE TO
QMA MALE



Low PIM Flexible Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5868				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	31
12"	24"	36"	48"	60"	50CM	Custom Len.	
$94.99	$101.99	$107.99	$115.99	$121.99	$98.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

N MALE TO QMA MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3C0049				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		32
12"	24"	36"	48"	60"	-	Custom Len.	
$63.99	$64.99	$65.99	$66.99	$67.99	-	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5874				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			33
12"	24"	36"	48"	60"	50CM	Custom Len.	
$96.99	$103.99	$111.99	$117.99	$123.99	$101.99	See Web	

N MALE TO QN MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38453				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	34
12"	24"	36"	48"	60"	72"	Custom Len.	
$82.99	$82.99	$83.99	$89.99	$85.99	$92.99	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE38452				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	35
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.99	$72.99	$73.99	$80.99	$81.99	$82.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE38450				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	36
12"	24"	36"	48"	60"	72"	Custom Len.	
$127.99	$129.99	$131.99	$133.99	$135.99	$137.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE38451				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	37
12"	24"	36"	48"	60"	72"	Custom Len.	
$82.99	$85.99	$89.99	$92.99	$96.99	$99.99	See Web	

N MALE TO QN MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38490				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	38
12"	24"	36"	48"	60"	72"	Custom Len.	
$86.99	$87.99	$88.99	$89.99	$90.99	$91.99	See Web	

LMR-195 Coax, 50 Ohm

Part No. PE3C0059				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		39
12"	24"	36"	48"	60"	-	Custom Len.	
$75.99	$76.99	$77.99	$78.99	$79.99	-	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE38489				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	40
12"	24"	36"	48"	60"	72"	Custom Len.	
$99.99	$101.99	$101.99	$103.99	$103.99	$103.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE38491				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	41
12"	24"	36"	48"	60"	72"	Custom Len.	
$113.99	$115.99	$117.99	$119.99	$121.99	$121.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE38492				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	42
12"	24"	36"	48"	60"	72"	Custom Len.	
$82.99	$91.99	$95.99	$93.99	$97.99	$101.99	See Web	

N MALE TO SHV PLUG



Standard Flexible Cable Assemblies

RG223/U Coax, 50 Ohm

Part No. PE3W04051				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	43
12"	24"	36"	48"	60"	50CM	Custom Len.	
$76.99	$80.99	$84.99	$88.99	$92.99	$78.99	See Web	

N MALE TO SMA MALE



Low PIM Flexible Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6213				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	44
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$64.99	$71.99	$78.99	$84.99	$62.99	See Web	

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C0253				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.32" dia.	7.2 dB/100ft		45
60"	72"	120"	-	-	-	Custom Len.	
$465.99	$515.00	$795.00	-	-	-	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5273				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			46
12"	24"	36"	48"	60"	50CM	Custom Len.	
$263.99	$289.99	$315.99	$341.99	$367.99	$279.99	See Web	

Low PIM Formable Cable Assemblies

PE-SR402FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2006				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.			47
30CM	45CM	50CM	-	100CM	150CM	Custom Len.	
Call	Call	Call	-	$97.99	Call	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5887				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			48
12"	24"	36"	48"	60"	50CM	Custom Len.	
$84.99	$91.99	$98.99	$105.99	$113.99	$89.99	See Web	

Test Flexible Cable Assemblies

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA1805				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			49
24"	36"	48"	-	-	-	Custom Len.	
$1,100.00	$1,170.00	$1,230.00	-	-	-	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE332				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	4.6 dB/100ft		50
12"	24"	36"	48"	60"	600"	Custom Len.	
$337.99	$369.99	$467.99	$435.99	$471.99	Call	See Web	

Part No. PE337				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			51
12"	24"	36"	48"	60"	72"	Custom Len.	
$325.99	$357.99	$391.99	$423.99	$457.99	$499.99	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3662				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	52
12"	24"	36"	48"	60"	72"	Custom Len.	
$52.99	$53.99	$55.99	$55.99	$57.99	$58.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3234				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		53
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.99	$65.99	$70.99	$73.99	$77.99	$81.99	See Web	

PE-P141 Coax, 50 Ohm

Part No. PE354				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.	11.2 dB/100ft	600 W	54
12"	24"	36"	48"	60"	72"	Custom Len.	
$205.99	$219.99	$233.99	$249.99	$263.99	$277.99	See Web	

PE-FF430 Coax, 50 Ohm

Part No. PE3C4008				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			55
60"	-	-	-	-	-	Custom Len.	
$850.00	-	-	-	-	-	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3C1982				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		56
12"	24"	36"	48"	60"	50CM	Custom Len.	
$48.99	$48.79	$49.99	$51.99	$52.99	$48.39	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

For our complete selection of cable assemblies, please visit our website

Standard Semi-Rigid Cable Assemblies

RG401/U Coax, 50 Ohm

Part No. PE3W04229				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	1,400 W	57
12"	24"	36"	48"	60"	50CM	Custom Len.	
$127.99	$155.99	$183.99	$213.99	$241.99	$145.99	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3887				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.1 dB/100ft	450 W	58
6"	12"	18"	24"	36"	48"	Custom Len.	
$86.99	$84.99	$95.99	$101.99	$103.99	$111.99	See Web	

N MALE TO
SMA MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5275				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			59
12"	24"	36"	48"	60"	50CM	Custom Len.	
$309.99	$335.99	$363.99	$389.99	$415.99	$327.99	See Web	

LMR-240-UF Coax, 50 Ohm

Part No. PE3W06417				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft		60
12"	24"	36"	48"	60"	50CM	Custom Len.	
$67.99	$69.99	$70.99	$72.99	$74.99	$68.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5892				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			61
12"	24"	36"	48"	60"	50CM	Custom Len.	
$86.99	$93.99	$101.99	$107.99	$115.99	$91.99	See Web	
Part No. PE3C6212				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	62
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.99	$70.99	$77.99	$83.99	$90.99	$67.99	See Web	

N MALE TO
SMA FEMALE



Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C1128				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		63
12"	24"	36"	48"	60"	50CM	Custom Len.	
$201.99	$221.99	$243.99	$263.99	$285.99	$215.99	See Web	

Test Flexible Cable Assemblies

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA1806						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						0.43" dia.			64
24"	36"	48"	-	-	-	Custom Len.			
$1,100.00	$1,160.00	$1,230.00	-	-	-	See Web			

Standard Flexible Cable Assemblies

PE-FF430 Coax, 50 Ohm

Part No. PE3C4009						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						0.43" dia.			65
60"	-	-	-	-	-	Custom Len.			
$850.00	-	-	-	-	-	See Web			

N MALE TO
SMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5277				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			66
12"	24"	36"	48"	60"	50CM	Custom Len.	
$283.99	$311.99	$337.99	$363.99	$389.99	$301.99	See Web	

N MALE TO
SSMC PLUG



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4432				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		67
6"	12"	18"	24"	36"	48"	Custom Len.	
$64.99	$71.99	$72.99	$66.99	$67.99	$68.99	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4451				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	68
6"	12"	18"	24"	36"	48"	Custom Len.	
$77.99	$81.99	$86.99	$90.99	$101.99	$109.99	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4399				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	69
6"	12"	18"	24"	36"	48"	Custom Len.	
$90.99	$91.99	$92.99	$92.99	$93.99	$94.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4415				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	70
6"	12"	18"	24"	36"	48"	Custom Len.	
$76.99	$86.99	$80.99	$82.99	$85.99	$89.99	See Web	

N MALE TO
SSMC PLUG RIGHT ANGLE



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4433				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		71
6"	12"	18"	24"	36"	48"	Custom Len.	
$61.99	$61.99	$62.99	$62.99	$62.99	$63.99	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4489				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	72
6"	12"	18"	24"	36"	48"	Custom Len.	
$73.99	$77.99	$82.99	$87.99	$96.99	$105.99	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4467				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	73
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.99	$81.99	$81.99	$82.99	$83.99	$84.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4416				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	74
6"	12"	18"	24"	36"	48"	Custom Len.	
$72.99	$74.99	$76.99	$77.99	$81.99	$84.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4478				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	75
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.99	$73.99	$75.99	$77.99	$80.99	$84.99	See Web	

N MALE TO
SSMC JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4452				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	76
6"	12"	18"	24"	36"	48"	Custom Len.	
$68.99	$73.99	$77.99	$82.99	$91.99	$101.99	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4400				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	77
6"	12"	18"	24"	36"	48"	Custom Len.	
$86.99	$95.99	$87.99	$96.99	$88.99	$90.99	See Web	

N MALE TO
TNC MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE35785				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	78
12"	24"	36"	48"	60"	-	Custom Len.	
$48.99	$49.99	$53.99	$54.99	$55.99	-	See Web	

PE-C200 Coax, 50 Ohm

Part No. PE36067				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10.8 dB/100ft	170 W	79
12"	24"	36"	48"	60"	-	Custom Len.	
$68.99	$69.99	$75.99	$80.99	$72.99	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

PE-C240 Coax, 50 Ohm

Part No. PE36958				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	80
12"	24"	36"	48"	60"	-	Custom Len.	
$63.99	$69.99	$71.99	$72.99	$74.99	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE34801				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	81
12"	24"	36"	48"	60"	-	Custom Len.	
$91.99	$92.99	$98.99	$103.99	$111.99	-	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE349				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft	820 W	82
12"	24"	36"	48"	60"	72"	Custom Len.	
$191.99	$211.99	$233.99	$253.99	$275.99	$297.99	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5267				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			83
12"	24"	36"	48"	60"	50CM	Custom Len.	
$263.99	$289.99	$315.99	$341.99	$367.99	$279.99	See Web	

LMR-400 Coax, 50 Ohm

Part No. PE3C0031				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		84
12"	24"	36"	48"	60"	-	Custom Len.	
$80.99	$81.99	$83.99	$85.99	$87.99	-	See Web	

Part No. PE3C0109				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		85
12"	24"	36"	48"	60"	-	Custom Len.	
$90.99	$92.99	$94.99	$90.99	$92.99	-	See Web	

Part No. PE3W00013				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.			86
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$61.99	$63.99	$65.99	$66.99	$61.99	See Web	

LMR-600-DB Coax, 50 Ohm

Part No. PE3W02356				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft		87
12"	24"	36"	48"	60"	50CM	Custom Len.	
$91.99	$95.99	$99.99	$103.99	$107.99	$94.99	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE335				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	4.6 dB/100ft		88
12"	24"	36"	48"	60"	50CM	Custom Len.	
$287.99	$321.99	$353.99	$387.99	$419.99	$309.99	See Web	

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE33927				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	89
12"	24"	36"	48"	60"	-	Custom Len.	
$99.99	$109.99	$119.99	$125.99	$135.99	-	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE33615				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	90
12"	24"	36"	48"	60"	72"	Custom Len.	
$87.99	$91.99	$89.99	$93.99	$96.99	$107.99	See Web	

RG8X Coax, 50 Ohm

Part No. PE37357				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13.5 dB/100ft	60 W	91
12"	24"	36"	48"	60"	-	Custom Len.	
$75.99	$84.99	$82.99	$86.99	$89.99	-	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3661				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	92
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.99	$56.99	$57.99	$58.99	$55.99	$60.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3652				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	93
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.99	$67.99	$74.99	$82.99	$90.99	$97.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE34272				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	94
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.99	$73.99	$74.99	$74.99	$75.99	$75.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE33455				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	95
12"	24"	36"	48"	60"	72"	Custom Len.	
$86.99	$87.99	$88.99	$89.99	$90.99	$97.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE33457				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	96
12"	24"	36"	48"	60"	72"	Custom Len.	
$74.99	$77.99	$80.99	$82.99	$85.99	$88.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3644				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	9 dB/100ft	190 W	97
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.99	$81.99	$83.99	$85.99	$87.99	$89.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3991				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	98
12"	24"	36"	48"	60"	72"	Custom Len.	
$99.99	$115.99	$117.99	$125.99	$133.99	$153.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3665				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	99
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.99	$62.99	$66.99	$70.99	$69.99	$78.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3989				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	1
12"	24"	36"	48"	60"	72"	Custom Len.	
$81.99	$85.99	$89.99	$86.99	$90.99	$93.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34266				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	2
12"	24"	36"	48"	60"	72"	Custom Len.	
$75.99	$78.99	$82.99	$85.99	$89.99	$92.99	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3982				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W	3
12"	24"	36"	48"	60"	72"	Custom Len.	
$109.99	$127.99	$145.99	$165.99	$183.99	$203.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3666				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	4
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.99	$81.99	$90.99	$101.99	$109.99	$119.99	See Web	

PE-FF430 Coax, 50 Ohm

Part No. PE3C4010				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			5
60"	-	-	-	-	-	Custom Len.	
$1,190.00	-	-	-	-	-	See Web	

Standard Semi-Rigid Cable Assemblies

PE-SR402AL Coax, 50 Ohm

Part No. PE3W05401				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					13 dB/100ft	450 W	6
12"	24"	36"	48"	60"	50CM	Custom Len.	
$96.99	$109.99	$119.99	$131.99	$143.99	$105.99	See Web	

RG401/U Coax, 50 Ohm

Part No. PE3W05651				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	1,400 W	7
12"	24"	36"	48"	60"	50CM	Custom Len.	
$157.99	$185.99	$213.99	$241.99	$269.99	$175.99	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3080				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.1 dB/100ft	450 W	8
12"	24"	36"	48"	60"	-	Custom Len.	
$107.99	$117.99	$119.99	$127.99	$135.99	-	See Web	

N MALE TO
TNC MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

LMR-200 Coax, 50 Ohm

Part No. PE3W02215				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10.5 dB/100ft		9
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.99	$66.99	$67.99	$68.99	$69.99	$66.99	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5268				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			10
12"	24"	36"	48"	60"	50CM	Custom Len.	
$337.99	$363.99	$389.99	$417.99	$443.99	$353.99	See Web	

N MALE TO
TNC FEMALE



Standard Flexible Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

PE-FF430 Coax, 50 Ohm

Part No. PE3C4011				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			11
60"	-	-	-	-	-	Custom Len.	
$1,190.00	-	-	-	-	-	See Web	

N MALE TO TNC FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C2276				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		12
12"	24"	36"	48"	60"	50CM	Custom Len.	
$235.99	$255.99	$275.99	$297.99	$317.99	$247.99	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5269				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			13
12"	24"	36"	48"	60"	50CM	Custom Len.	
$295.99	$323.99	$349.99	$375.99	$401.99	$313.99	See Web	

N MALE TO REVERSE POLARITY TNC MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE36362				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	14
12"	24"	36"	48"	60"	-	Custom Len.	
$51.99	$52.99	$52.99	$53.99	$54.99	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE34966				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	15
12"	24"	36"	48"	60"	-	Custom Len.	
$79.99	$80.99	$87.99	$84.99	$85.99	-	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE34554				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	16
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.99	$65.99	$61.99	$62.99	$62.99	$63.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE34573				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	17
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.99	$67.99	$74.99	$81.99	$88.99	$95.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE35241				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	18
12"	24"	36"	48"	60"	72"	Custom Len.	
$89.99	$90.99	$92.99	$93.99	$94.99	$95.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE35243				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	19
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.99	$74.99	$77.99	$80.99	$82.99	$85.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE35245				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	20
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.99	$56.99	$63.99	$63.99	$66.99	$70.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE35247				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	21
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.99	$81.99	$84.99	$88.99	$92.99	$95.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34626				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	22
12"	24"	36"	48"	60"	-	Custom Len.	
$68.99	$84.99	$94.99	$103.99	$113.99	-	See Web	

N MALE TO REVERSE POLARITY TNC MALE



Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE36283				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	23
12"	24"	36"	48"	60"	-	Custom Len.	
$83.99	$92.99	$101.99	$117.99	$117.99	-	See Web	

N MALE TO UMCX PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38813				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	24
3"	6"	9"	12"	18"	24"	Custom Len.	
$89.99	$89.99	$89.99	$94.99	$95.99	$90.99	See Web	

N MALE TO NEX10 MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6256				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	25
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.99	$79.99	$86.99	$93.99	$101.99	$77.99	See Web	

N MALE RIGHT ANGLE TO BNC MALE



Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE3W06095				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	26
12"	24"	36"	48"	60"	50CM	Custom Len.	
$77.99	$86.99	$96.99	$105.99	$115.99	$83.99	See Web	

N MALE RIGHT ANGLE TO BNC MALE RIGHT ANGLE



Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE3W00447				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	27
12"	24"	36"	48"	60"	50CM	Custom Len.	
$99.99	$109.99	$117.99	$125.99	$135.99	$105.99	See Web	

N MALE RIGHT ANGLE TO N MALE



Standard Flexible Cable Assemblies

LMR-400 Coax, 50 Ohm

Part No. PE3C7931				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		28
12"	24"	36"	48"	60"	50CM	Custom Len.	
$67.99	$69.99	$70.99	$72.99	$73.99	$66.99	See Web	

LMR-195 Coax, 50 Ohm

Part No. PE3C0120				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		29
12"	24"	36"	48"	60"	-	Custom Len.	
$61.99	$59.99	$63.99	$60.99	$61.99	-	See Web	

N MALE RIGHT ANGLE TO N MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE36910				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	30
12"	24"	36"	48"	60"	-	Custom Len.	
$84.99	$91.99	$92.99	$86.99	$87.99	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE38699				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	31
36"	48"	60"	72"	120"	-	Custom Len.	
$109.99	$111.99	$113.99	$115.99	$127.99	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE38194				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	32
36"	48"	60"	72"	120"	-	Custom Len.	
$145.99	$147.99	$149.99	$147.99	$171.99	-	See Web	

LMR-400 Coax, 50 Ohm

Part No. PE3C0107				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		33
12"	24"	36"	48"	60"	-	Custom Len.	
$105.99	$103.99	$107.99	$109.99	$107.99	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

LMR-195 Coax, 50 Ohm

Part No. PE3C0119				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		34
12"	24"	36"	48"	60"	-	Custom Len.	
$64.99	$65.99	$66.99	$65.99	$66.99	-	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE3C0967				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		35
12"	24"	36"	48"	60"	50CM	Custom Len.	
$415.99	$437.99	$457.99	$477.99	$499.99	$429.99	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5287				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			36
12"	24"	36"	48"	60"	50CM	Custom Len.	
$413.99	$439.99	$465.99	$491.99	$520.00	$429.99	See Web	

Precision Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39444				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	37
6"	9"	12"	18"	24"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39458				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	38
6"	9"	12"	18"	24"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7968				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			39
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.99	$69.99	$73.99	$78.99	$83.99	$62.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8000				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			40
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$62.99	$65.99	$67.99	$70.99	$59.99	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7846				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		41
12"	50CM	24"	36"	48"	60"	Custom Len.	
$75.99	$78.99	$79.99	$84.99	$88.99	$92.99	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4145				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	42
12"	24"	36"	48"	60"	50CM	Custom Len.	
$117.99	$121.99	$129.99	$135.99	$143.99	$121.99	See Web	

Part No. PE3C6206				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	43
12"	24"	36"	48"	60"	50CM	Custom Len.	
$71.99	$78.99	$85.99	$92.99	$99.99	$75.99	See Web	

SPO-500 Coax, 50 Ohm

Part No. PE3C6373				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.53" dia.			44
12"	24"	36"	48"	60"	50CM	Custom Len.	
$56.99	$60.99	$63.99	$66.99	$70.99	$59.99	See Web	

SPF-500 Coax, 50 Ohm

Part No. PE3C6376				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.			45
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$62.99	$67.99	$72.99	$77.99	$61.99	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3233				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		46
12"	24"	36"	48"	60"	50CM	Custom Len.	
$431.99	$465.99	$497.99	$535.00	$565.00	$453.99	See Web	

Standard Formable Cable Assemblies

PE-SR401FL Coax, 50 Ohm

Part No. PE34680				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	47
12"	24"	36"	48"	60"	-	Custom Len.	
$139.99	$149.99	$169.99	$187.99	$205.99	-	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE33977				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	48
12"	24"	36"	48"	60"	-	Custom Len.	
$93.99	$103.99	$111.99	$119.99	$129.99	-	See Web	

Part No. PE39452				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	400 W	49
6"	9"	12"	18"	24"	-	Custom Len.	
$93.99	$96.99	$98.99	Call	Call	-	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39466				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	50
6"	9"	12"	18"	24"	-	Custom Len.	
$94.99	Call	$94.99	$99.99	$105.99	-	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE33974				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	51
12"	24"	36"	48"	60"	72"	Custom Len.	
$135.99	$139.99	$143.99	$139.99	$143.99	$153.99	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3698				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	52
12"	24"	36"	48"	60"	72"	Custom Len.	
$97.99	$92.99	$99.99	$94.99	$95.99	$103.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE34231				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	53
12"	24"	36"	48"	60"	72"	Custom Len.	
$88.99	$89.99	$90.99	$90.99	$91.99	$91.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34238				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	54
12"	24"	36"	48"	60"	72"	Custom Len.	
$105.99	$98.99	$111.99	$105.99	$107.99	$109.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3272				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	9 dB/100ft	190 W	55
12"	24"	36"	48"	60"	72"	Custom Len.	
$131.99	$125.99	$127.99	$137.99	$131.99	$133.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3781				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	56
12"	24"	36"	48"	60"	72"	Custom Len.	
$147.99	$165.99	$165.99	$175.99	$195.99	$205.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3882				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	57
12"	24"	36"	48"	60"	72"	Custom Len.	
$103.99	$99.99	$103.99	$107.99	$111.99	$113.99	See Web	

RG225/U Coax, 50 Ohm

Part No. PE34222				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	58
12"	24"	36"	48"	60"	72"	Custom Len.	
$175.99	$215.99	$255.99	$327.99	$335.99	$375.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34236				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	59
12"	24"	36"	48"	60"	72"	Custom Len.	
$96.99	$101.99	$105.99	$107.99	$111.99	$123.99	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3268				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	60
12"	24"	36"	48"	60"	72"	Custom Len.	
$143.99	$171.99	$191.99	$213.99	$233.99	$253.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3412				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	61
12"	24"	36"	48"	60"	72"	Custom Len.	
$113.99	$121.99	$131.99	$139.99	$139.99	$159.99	See Web	

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1049				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			62
12"	24"	36"	50CM	100CM	-	Custom Len.	
$131.99	$147.99	$167.99	Call	$173.99	-	See Web	

N MALE RIGHT ANGLE TO N FEMALE



Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7847				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		63
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.99	$76.99	$80.99	$85.99	$89.99	$75.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6203				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	64
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.99	$73.99	$79.99	$86.99	$93.99	$70.99	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3115				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		65
12"	24"	36"	48"	60"	50CM	Custom Len.	
$417.99	$449.99	$483.99	$520.00	$550.00	$437.99	See Web	

Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE3W06096				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	66
12"	24"	36"	48"	60"	50CM	Custom Len.	
$86.99	$96.99	$105.99	$115.99	$123.99	$92.99	See Web	

N MALE RIGHT ANGLE TO
N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C0673				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		67
12"	24"	36"	48"	60"	50CM	Custom Len.	
$337.99	$357.99	$377.99	$397.99	$417.99	$349.99	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5286				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			68
12"	24"	36"	48"	60"	50CM	Custom Len.	
$371.99	$397.99	$423.99	$449.99	$477.99	$387.99	See Web	

LMR-240-UF Coax, 50 Ohm

Part No. PE3W06441				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft		69
12"	24"	36"	48"	60"	50CM	Custom Len.	
$98.99	$99.99	$101.99	$103.99	$105.99	$99.99	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7848				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		70
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.99	$76.99	$80.99	$85.99	$89.99	$75.99	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6204				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	71
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.99	$73.99	$79.99	$86.99	$93.99	$70.99	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C2953				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		72
12"	24"	36"	48"	60"	50CM	Custom Len.	
$447.99	$479.99	$515.00	$545.00	$580.00	$467.99	See Web	

Standard Formable Cable Assemblies

PE-SR401FL Coax, 50 Ohm

Part No. PE39082				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	73
12"	24"	36"	48"	60"	-	Custom Len.	
$119.99	$135.99	$153.99	$169.99	$187.99	-	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE38670				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	74
12"	24"	36"	48"	60"	-	Custom Len.	
$105.99	$107.99	$117.99	$123.99	$131.99	-	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3407				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	75
12"	24"	36"	48"	60"	72"	Custom Len.	
$88.99	$88.99	$83.99	$84.99	$85.99	$86.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE33021				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		76
12"	24"	36"	48"	60"	72"	Custom Len.	
$90.99	$92.99	$99.99	$107.99	$121.99	$121.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE34229				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	77
12"	24"	36"	48"	60"	72"	Custom Len.	
$89.99	$90.99	$90.99	$91.99	$92.99	$92.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34218				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	78
12"	24"	36"	48"	60"	72"	Custom Len.	
$91.99	$93.99	$96.99	$99.99	$101.99	$105.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE33545				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	79
12"	24"	36"	48"	60"	72"	Custom Len.	
$117.99	$119.99	$121.99	$121.99	$123.99	$125.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE33178				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	80
12"	24"	36"	48"	60"	72"	Custom Len.	
$109.99	$117.99	$125.99	$135.99	$143.99	$153.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE33536				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	81
12"	24"	36"	48"	60"	72"	Custom Len.	
$76.99	$85.99	$84.99	$87.99	$91.99	$101.99	See Web	

RG225/U Coax, 50 Ohm

Part No. PE34221				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	82
12"	24"	36"	48"	60"	72"	Custom Len.	
$139.99	$179.99	$219.99	$259.99	$299.99	$339.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34214				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	83
12"	24"	36"	48"	60"	72"	Custom Len.	
$92.99	$95.99	$99.99	$103.99	$107.99	$111.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34227				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	26.1 dB/100ft	160 W	84
12"	24"	36"	48"	60"	72"	Custom Len.	
$96.99	$101.99	$105.99	$107.99	$111.99	$115.99	See Web	

RG393/U Coax, 50 Ohm

Part No. PE33532				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	85
12"	24"	36"	48"	60"	72"	Custom Len.	
$117.99	$133.99	$153.99	$171.99	$191.99	$209.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE33528				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	86
12"	24"	36"	48"	60"	72"	Custom Len.	
$94.99	$103.99	$117.99	$125.99	$127.99	$135.99	See Web	

LMR-400 Coax, 50 Ohm

Part No. PE3W03991				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		87
12"	24"	36"	48"	60"	50CM	Custom Len.	
$89.99	$91.99	$92.99	$94.99	$95.99	$90.99	See Web	

N MALE RIGHT ANGLE TO
SMA MALE



Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5279				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			88
12"	24"	36"	48"	60"	50CM	Custom Len.	
$337.99	$363.99	$389.99	$417.99	$443.99	$353.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6209				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	89
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$67.99	$74.99	$80.99	$87.99	$64.99	See Web	

N MALE RIGHT ANGLE TO
SMA MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5281				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			90
12"	24"	36"	48"	60"	50CM	Custom Len.	
$385.99	$411.99	$437.99	$463.99	$491.99	$401.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6211				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	91
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.99	$73.99	$79.99	$86.99	$93.99	$70.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

N MALE RIGHT ANGLE TO SMA FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5280				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			92
12"	24"	36"	48"	60"	50CM	Custom Len.	
$359.99	$385.99	$411.99	$439.99	$465.99	$375.99	See Web	

N MALE RIGHT ANGLE TO TNC MALE



Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5282				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			93
12"	24"	36"	48"	60"	50CM	Custom Len.	
$337.99	$363.99	$389.99	$417.99	$443.99	$353.99	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3243				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		94
12"	24"	36"	48"	60"	50CM	Custom Len.	
$483.99	$515.00	$550.00	$580.00	$615.00	$505.00	See Web	

Standard Flexible Cable Assemblies

LMR-600-DB Coax, 50 Ohm

Part No. PE3C4750				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft		95
12"	24"	36"	48"	60"	50CM	Custom Len.	
$105.99	$101.99	$105.99	$109.99	$113.99	$101.99	See Web	

N MALE RIGHT ANGLE TO TNC MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3W00020				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		96
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.99	$73.99	$74.99	$75.99	$76.99	$73.99	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE3C1271				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		97
12"	24"	36"	48"	60"	50CM	Custom Len.	
$441.99	$437.99	$457.99	$477.99	$499.99	$429.99	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5284				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			98
12"	24"	36"	48"	60"	50CM	Custom Len.	
$413.99	$439.99	$465.99	$491.99	$520.00	$429.99	See Web	

N MALE RIGHT ANGLE TO TNC FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5283				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			99
12"	24"	36"	48"	60"	50CM	Custom Len.	
$371.99	$397.99	$423.99	$449.99	$477.99	$387.99	See Web	

N MALE RIGHT ANGLE TO NEX10 MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6257				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	1
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.99	$82.99	$89.99	$96.99	$103.99	$80.99	See Web	

N FEMALE TO N MALE



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39460				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	2
6"	9"	12"	18"	24"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39468				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	3
6"	9"	12"	18"	24"	-	Custom Len.	
Call	$105.99	$107.99	Call	$111.99	-	See Web	

N FEMALE TO N FEMALE



Low Loss Flexible Cable Assemblies

LMR-600-DB Coax, 50 Ohm

Part No. PE3W05453				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft		4
12"	48"	60"	50CM	150CM	-	Custom Len.	
$93.99	$99.99	$103.99	$91.99	$103.99	-	See Web	

Low PIM Flexible Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3W07489				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			5
12"	24"	36"	48"	60"	50CM	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3234				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		6
12"	24"	36"	48"	60"	50CM	Custom Len.	
$343.99	$375.99	$407.99	$439.99	$471.99	$365.99	See Web	

Standard Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C0126				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		7
12"	24"	36"	48"	60"	-	Custom Len.	
$179.99	$165.99	$187.99	$173.99	$177.99	-	See Web	

N FEMALE TO N FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3247				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		8
12"	24"	36"	48"	60"	50CM	Custom Len.	
$409.99	$441.99	$473.99	$510.00	$540.00	$429.99	See Web	

Standard Flexible Cable Assemblies

PE-P195 Coax, 50 Ohm

Part No. PE3W02976				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	9
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.99	$79.99	$92.99	$105.99	$119.99	$74.99	See Web	

N FEMALE TO NMO MOUNT SEXLESS



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37851				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	10
60"	120"	180"	-	-	-	Custom Len.	
$59.99	$63.99	$74.99	-	-	-	See Web	

N FEMALE TO QN MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38457				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	11
12"	24"	36"	48"	60"	72"	Custom Len.	
$83.99	$84.99	$84.99	$85.99	$86.99	$87.99	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE38456				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	12
12"	24"	36"	48"	60"	72"	Custom Len.	
$79.99	$80.99	$81.99	$82.99	$82.99	$83.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

RG213/U Coax, 50 Ohm

Part No. PE38454				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	13
12"	24"	36"	48"	60"	72"	Custom Len.	
$127.99	$129.99	$131.99	$133.99	$135.99	$137.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE38455				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	14
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.99	$81.99	$85.99	$89.99	$92.99	$96.99	See Web	

N FEMALE TO QN MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38494				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	15
12"	24"	36"	48"	60"	72"	Custom Len.	
$83.99	$84.99	$85.99	$86.99	$87.99	$97.99	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE38493				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	16
12"	24"	36"	48"	60"	72"	Custom Len.	
$95.99	$96.99	$97.99	$98.99	$99.99	$99.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE38495				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	17
12"	24"	36"	48"	60"	72"	Custom Len.	
$111.99	$113.99	$115.99	$117.99	$119.99	$121.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE38496				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	18
12"	24"	36"	48"	60"	72"	Custom Len.	
$83.99	$87.99	$91.99	$94.99	$98.99	$101.99	See Web	

N FEMALE TO SMA MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6215				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	19
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$64.99	$71.99	$78.99	$84.99	$62.99	See Web	

N FEMALE TO SMA MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

LMR-240-UF Coax, 50 Ohm

Part No. PE3W04423				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft		20
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.99	$67.99	$69.99	$71.99	$72.99	$67.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6217				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	21
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.99	$70.99	$77.99	$83.99	$90.99	$67.99	See Web	

N FEMALE TO TNC MALE



Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3244				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		22
12"	24"	36"	48"	60"	50CM	Custom Len.	
$313.99	$345.99	$377.99	$409.99	$441.99	$333.99	See Web	

N FEMALE BULKHEAD TO MCX PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 419



Precision Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39449				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	23
6"	9"	12"	18"	24"	-	Custom Len.	
$62.99	Call	Call	$76.99	Call	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39463				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	24
6"	9"	12"	18"	24"	36"	Custom Len.	
$60.99	$60.99	Call	$65.99	$69.99	Call	See Web	

N FEMALE BULKHEAD TO MMCX PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 419



Precision Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39464				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	25
6"	9"	12"	18"	24"	30"	Custom Len.	
$60.99	$63.99	$60.99	$65.99	$70.99	Call	See Web	

N FEMALE BULKHEAD TO N MALE

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Flexible Cable Assemblies

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1050				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			26
12"	24"	36"	50CM	100CM	-	Custom Len.	
$115.99	$135.99	$157.99	Call	$163.99	-	See Web	

N FEMALE BULKHEAD TO N MALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3W03365				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	27
12"	24"	36"	48"	60"	50CM	Custom Len.	
$93.99	$105.99	$115.99	$125.99	$135.99	$101.99	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE34216				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	28
12"	24"	36"	48"	60"	72"	Custom Len.	
$113.99	$117.99	$121.99	$123.99	$125.99	$129.99	See Web	

N FEMALE BULKHEAD TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C1000				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		29
12"	24"	36"	48"	60"	50CM	Custom Len.	
$283.99	$303.99	$323.99	$343.99	$363.99	$297.99	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5256				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			30
12"	24"	36"	48"	60"	50CM	Custom Len.	
$329.99	$355.99	$383.99	$409.99	$435.99	$347.99	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3232				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		31
12"	24"	36"	48"	60"	50CM	Custom Len.	
$333.99	$365.99	$397.99	$429.99	$461.99	$353.99	See Web	

N FEMALE BULKHEAD TO QMA MALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4238				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	32
12"	24"	36"	48"	60"	50CM	Custom Len.	
$81.99	$84.99	$88.99	$92.99	$96.99	$83.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

N FEMALE BULKHEAD TO SMA MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5274				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			33
12"	24"	36"	48"	60"	50CM	Custom Len.	
$295.99	$323.99	$349.99	$375.99	$401.99	$313.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6214				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	34
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$64.99	$71.99	$78.99	$84.99	$62.99	See Web	

N FEMALE BULKHEAD TO SMA MALE RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5276				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			35
12"	24"	36"	48"	60"	50CM	Custom Len.	
$343.99	$369.99	$395.99	$423.99	$449.99	$359.99	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6216				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	36
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.99	$70.99	$77.99	$83.99	$90.99	$67.99	See Web	

Standard Flexible Cable Assemblies

PE-P195 Coax, 50 Ohm

Part No. PE3W06405				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	37
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.99	$76.99	$89.99	$103.99	$115.99	$72.99	See Web	

N FEMALE BULKHEAD TO SMA FEMALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

LMR-400-UF Coax, 50 Ohm

Part No. PE3W05630				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	5 dB/100ft		38
12"	24"	36"	48"	60"	50CM	Custom Len.	
$107.99	$111.99	$113.99	$117.99	$121.99	$109.99	See Web	

N FEMALE BULKHEAD TO SMA FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5278				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			39
12"	24"	36"	48"	60"	50CM	Custom Len.	
$317.99	$317.99	$317.99	$317.99	$317.99	$317.99	See Web	

N FEMALE BULKHEAD TO REVERSE POLARITY SMA MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE3C5030				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	40
12"	24"	36"	48"	60"	50CM	Custom Len.	
$103.99	$107.99	$115.99	$123.99	$131.99	$103.99	See Web	

N FEMALE BULKHEAD TO SMP FEMALE RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3W04763				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	41
12"	24"	36"	48"	60"	50CM	Custom Len.	
$90.99	$91.99	$93.99	$94.99	$95.99	$91.99	See Web	

N FEMALE BULKHEAD TO TNC MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C1110				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		42
12"	24"	36"	48"	60"	50CM	Custom Len.	
$239.99	$259.99	$281.99	$299.99	$319.99	$253.99	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5270				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			43
12"	24"	36"	48"	60"	50CM	Custom Len.	
$295.99	$323.99	$349.99	$375.99	$401.99	$313.99	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C1084				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		44
12"	24"	36"	48"	60"	50CM	Custom Len.	
$323.99	$355.99	$387.99	$419.99	$453.99	$345.99	See Web	

N FEMALE BULKHEAD TO TNC MALE RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

LMR-240 Coax, 50 Ohm

Part No. PE3W00415				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		45
12"	24"	36"	48"	60"	50CM	Custom Len.	
$67.99	$68.99	$69.99	$71.99	$72.99	$68.99	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5271				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			46
12"	24"	36"	48"	60"	50CM	Custom Len.	
$371.99	$397.99	$423.99	$449.99	$477.99	$387.99	See Web	

N FEMALE BULKHEAD TO TNC FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5272				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			47
12"	24"	36"	48"	60"	50CM	Custom Len.	
$329.99	$355.99	$383.99	$409.99	$435.99	$347.99	See Web	

N FEMALE BULKHEAD TO HMCX32 1.2 PLUG



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1015				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			48
3"	6"	12"	-	-	-	Custom Len.	
Call	$26.59	Call	-	-	-	See Web	

N FEMALE BULKHEAD TO UMCX 2.1 PLUG



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1013				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			49
3"	6"	12"	-	-	-	Custom Len.	
Call	Call	$26.59	-	-	-	See Web	

N FEMALE BULKHEAD TO UMCX 2.5 PLUG



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3CA1011				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.07" dia.			50
3"	6"	9"	12"	-	-	Custom Len.	
Call	$24.59	$22.99	$24.59	-	-	See Web	

RG178-DS Coax, 50 Ohm

Part No. PE3CA1012				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.086" dia.			51
3"	6"	9"	12"	-	-	Custom Len.	
Call	$22.99	$27.99	Call	-	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

PE-81mm Coax, 50 Ohm

Part No. PE3CA1008				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.032" dia.		
3"	6"	12"	-	-	-	Custom Len.
Call	$22.99	Call	-	-	-	See Web

52

PE-113mm Coax, 50 Ohm

Part No. PE3CA1009				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.044" dia.		
3"	6"	12"	-	-	-	Custom Len.
Call	$22.99	$26.59	-	-	-	See Web

53

PE-137mm Coax, 50 Ohm

Part No. PE3CA1010				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.053" dia.		
3"	6"	12"	-	-	-	Custom Len.
Call	$22.99	$26.59	-	-	-	See Web

54

N FEMALE BULKHEAD TO WMCX 1.6 PLUG



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1014				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.032" dia.		
3"	6"	12"	-	-	-	Custom Len.
Call	Call	$25.59	-	-	-	See Web

55

N FEMALE BULKHEAD TO NEX10 MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6255					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.99	$79.99	$86.99	$93.99	$101.99	$77.99	See Web	

56

N FEMALE 4 HOLE FLANGE TO MMCX PLUG RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C0063					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.11" dia.	24 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.	
$71.99	$67.99	$67.99	$68.99	$69.99	-	See Web	

57

NEX10 MALE TO NEX10 MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7972					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$79.99	$84.99	$88.99	$93.99	$97.99	$78.99	See Web	

58

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8004					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.99	$77.99	$80.99	$82.99	$85.99	$74.99	See Web	

59

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7850					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.303" dia.	5.85 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$86.99	$90.99	$94.99	$99.99	$103.99	$88.99	See Web	

60

NEX10 MALE TO NEX10 FEMALE



Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7851					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.303" dia.	5.85 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.99	$80.99	$84.99	$88.99	$93.99	$78.99	See Web	

61

NEX10 MALE TO NEX10 FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7852				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$79.99	$83.99	$87.99	$92.99	$96.99	$81.99	See Web

62

NEX10 MALE RIGHT ANGLE TO NEX10 FEMALE



Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7854				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$82.99	$86.99	$90.99	$95.99	$99.99	$85.99	See Web

63

NEX10 MALE RIGHT ANGLE TO NEX10 FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7855				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$85.99	$89.99	$94.99	$98.99	$103.99	$88.99	See Web

64

NEX10 MALE RIGHT ANGLE TO NEX10 MALE RIGHT ANGLE



Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7853				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$92.99	$96.99	$101.99	$105.99	$109.99	$95.99	See Web

65

NMO MOUNT SEXLESS TO TNC MALE



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37848				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
60"	120"	180"	-	-	-	Custom Len.
$58.99	$58.99	$62.99	-	-	-	See Web

66

QMA MALE TO QMA MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38272				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W
12"	24"	36"	48"	60"	72"	Custom Len.
$63.99	$64.99	$69.99	$66.99	$67.99	$72.99	See Web

67

Low PIM Flexible Cable Assemblies

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8005				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$47.79	$50.99	$52.99	$55.99	$57.99	$46.79	See Web

68

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5869				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$89.99	$96.99	$103.99	$111.99	$117.99	$93.99	See Web

69

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE38271				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	72"	Custom Len.
$71.99	$71.99	$72.99	$73.99	$74.99	$75.99	See Web

70

For our complete selection of cable assemblies, please visit our website

RG316/U Coax, 50 Ohm

Part No. PE38270				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	71
12"	24"	36"	48"	60"	72"	Custom Len.	
$76.99	$79.99	$88.99	$87.99	$96.99	$94.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE38161				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	72
12"	24"	36"	48"	60"	72"	Custom Len.	
$119.99	$121.99	$125.99	$129.99	$131.99	$135.99	See Web	

QMA MALE TO QMA MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7974				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			73
12"	24"	36"	48"	60"	50CM	Custom Len.	
$56.99	$60.99	$65.99	$69.99	$74.99	$55.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8006					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.16" dia.			74
12"	19.680	24"	36"	48"	60"	Custom Len.		
$52.99	Call	$55.99	$57.99	$59.99	$61.99	See Web		

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7871				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		75
12"	24"	36"	48"	60"	50CM	Custom Len.	
$67.99	$72.99	$76.99	$80.99	$85.99	$70.99	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5875				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			76
12"	24"	36"	48"	60"	50CM	Custom Len.	
$92.99	$99.99	$107.99	$113.99	$121.99	$96.99	See Web	

QMA MALE TO QMA FEMALE



Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7872				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		77
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.99	$67.99	$71.99	$75.99	$80.99	$65.99	See Web	

QMA MALE TO QMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7873				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		78
12"	24"	36"	48"	60"	50CM	Custom Len.	
$51.99	$55.99	$59.99	$63.99	$68.99	$53.99	See Web	

QMA MALE TO SMA MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5870				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			79
12"	24"	36"	48"	60"	50CM	Custom Len.	
$80.99	$87.99	$94.99	$101.99	$109.99	$84.99	See Web	

QMA MALE TO SMA FEMALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5882				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			80
12"	24"	36"	48"	60"	50CM	Custom Len.	
$81.99	$88.99	$95.99	$103.99	$109.99	$85.99	See Web	

QMA MALE RIGHT ANGLE TO QMA MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7975				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			81
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.99	$69.99	$73.99	$78.99	$83.99	$62.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8007					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.16" dia.			82
12"	19.680	24"	36"	48"	60"	Custom Len.		
$60.99	Call	$62.99	$65.99	$67.99	$70.99	See Web		

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7874				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		83
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.99	$77.99	$81.99	$85.99	$90.99	$75.99	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5877				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			84
12"	24"	36"	48"	60"	50CM	Custom Len.	
$94.99	$101.99	$109.99	$115.99	$121.99	$99.99	See Web	

QMA MALE RIGHT ANGLE TO QMA FEMALE



Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7875				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		85
12"	24"	36"	48"	60"	50CM	Custom Len.	
$67.99	$72.99	$76.99	$80.99	$85.99	$70.99	See Web	

QMA MALE RIGHT ANGLE TO QMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7876				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		86
12"	24"	36"	48"	60"	50CM	Custom Len.	
$56.99	$60.99	$64.99	$68.99	$72.99	$58.99	See Web	

QMA MALE RIGHT ANGLE TO SMA MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5876				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			87
12"	24"	36"	48"	60"	50CM	Custom Len.	
$83.99	$90.99	$97.99	$105.99	$111.99	$87.99	See Web	

Standard Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3W06662				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		88
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.99	$71.99	$72.99	$73.99	$73.99	$71.99	See Web	

QMA MALE RIGHT ANGLE TO SMA MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

LMR-240-UF Coax, 50 Ohm

Part No. PE3W08640				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft		89
60"	50CM	-	-	-	-	Custom Len.	
$85.99	$80.99	-	-	-	-	See Web	

QN MALE TO QN MALE



Low Loss Flexible Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

PE-C195 Coax, 50 Ohm

Part No. PE38449	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	11.3 dB/100ft	150 W

12"	24"	36"	48"	60"	72"	Custom Len.
$101.99	$101.99	$103.99	$103.99	$105.99	$105.99	See Web

90

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE38448	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	20 dB/100ft	44 W

12"	24"	36"	48"	60"	72"	Custom Len.
$98.99	$99.99	$101.99	$101.99	$103.99	$103.99	See Web

91

RG213/U Coax, 50 Ohm

Part No. PE38446	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.405" dia.	8 dB/100ft	190 W

12"	24"	36"	48"	60"	72"	Custom Len.
$185.99	$187.99	$189.99	$191.99	$193.99	$195.99	See Web

92

RG223/U Coax, 50 Ohm

Part No. PE38447	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.21" dia.	13.4 dB/100ft	53 W

12"	24"	36"	48"	60"	72"	Custom Len.
$99.99	$103.99	$107.99	$111.99	$115.99	$119.99	See Web

93

QN MALE TO QN MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38486	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	11.3 dB/100ft	150 W

12"	24"	36"	48"	60"	72"	Custom Len.
$103.99	$105.99	$105.99	$107.99	$107.99	$107.99	See Web

94

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE38485	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	20 dB/100ft	44 W

12"	24"	36"	48"	60"	72"	Custom Len.
$119.99	$121.99	$121.99	$123.99	$123.99	$125.99	See Web

95

RG213/U Coax, 50 Ohm

Part No. PE38487	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.405" dia.	8 dB/100ft	190 W

12"	24"	36"	48"	60"	72"	Custom Len.
$169.99	$171.99	$173.99	$175.99	$177.99	$179.99	See Web

96

RG223/U Coax, 50 Ohm

Part No. PE38488	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.21" dia.	13.4 dB/100ft	53 W

12"	24"	36"	48"	60"	72"	Custom Len.
$105.99	$109.99	$113.99	$117.99	$121.99	$121.99	See Web

97

QN MALE RIGHT ANGLE TO N FEMALE



Standard Flexible Cable Assemblies

LMR-400 Coax, 50 Ohm

Part No. PE3W04619	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.405" dia.	4.25 dB/100ft	

12"	24"	36"	48"	60"	50CM	Custom Len.
$111.99	$111.99	$113.99	$115.99	$117.99	$111.99	See Web

98

SC MALE TO SC MALE



Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE34443	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.405" dia.	8 dB/100ft	190 W

12"	24"	36"	48"	60"	72"	Custom Len.
$191.99	$205.99	$197.99	$213.99	$205.99	$207.99	See Web

99

RG58C/U Coax, 50 Ohm

Part No. PE3104	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	20 dB/100ft	44 W

12"	24"	36"	48"	60"	72"	Custom Len.
$291.99	$291.99	$293.99	$293.99	$295.99	$295.99	See Web

1

RG141A/U Coax, 50 Ohm

Part No. PE34439	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.19" dia.	13 dB/100ft	650 W

12"	24"	36"	48"	60"	72"	Custom Len.
$307.99	$315.99	$323.99	$331.99	$339.99	$347.99	See Web

2

RG142B/U Coax, 50 Ohm

Part No. PE3334	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	13 dB/100ft	650 W

12"	24"	36"	48"	60"	72"	Custom Len.
$289.99	$295.99	$303.99	$309.99	$317.99	$323.99	See Web

3

RG213/U Coax, 50 Ohm

Part No. PE3395	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.405" dia.	8 dB/100ft	190 W

12"	24"	36"	48"	60"	72"	Custom Len.
$175.99	$177.99	$179.99	$181.99	$183.99	$185.99	See Web

4

RG214/U Coax, 50 Ohm

Part No. PE3409	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.425" dia.	7.32 dB/100ft	190 W

12"	24"	36"	48"	60"	72"	Custom Len.
$193.99	$201.99	$211.99	$219.99	$229.99	$237.99	See Web

5

RG223/U Coax, 50 Ohm

Part No. PE3348	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.21" dia.	13.4 dB/100ft	53 W

12"	24"	36"	48"	60"	72"	Custom Len.
$287.99	$289.99	$293.99	$297.99	$301.99	$303.99	See Web

6

RG225/U Coax, 50 Ohm

Part No. PE34447	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.43" dia.		1,700 W

12"	24"	36"	48"	60"	72"	Custom Len.
$241.99	$269.99	$311.99	$351.99	$393.99	$435.99	See Web

7

RG393/U Coax, 50 Ohm

Part No. PE3416	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.39" dia.	8.8 dB/100ft	1,700 W

12"	24"	36"	48"	60"	72"	Custom Len.
$205.99	$237.99	$257.99	$263.99	$281.99	$301.99	See Web

8

RG400/U Coax, 50 Ohm

Part No. PE34453	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	14.7 dB/100ft	650 W

12"	24"	36"	48"	60"	72"	Custom Len.
$299.99	$307.99	$315.99	$323.99	$333.99	$341.99	See Web

9

RG59B/U Coax, 75 Ohm

Part No. PE34441	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.242" dia.	11.5 dB/100ft	77 W

12"	24"	36"	48"	60"	72"	Custom Len.
$291.99	$291.99	$293.99	$295.99	$295.99	$297.99	See Web

10

RG62A/U Coax, 93 Ohm

Part No. PE34449	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.242" dia.	13 dB/100ft	77 W

12"	24"	36"	48"	60"	72"	Custom Len.
$297.99	$299.99	$301.99	$301.99	$303.99	$305.99	See Web

11

SHV PLUG TO SHV PLUG



Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE33068	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.405" dia.	8 dB/100ft	190 W

12"	24"	36"	48"	60"	72"	Custom Len.
$131.99	$127.99	$129.99	$133.99	$137.99	$149.99	See Web

12

RG58C/U Coax, 50 Ohm

Part No. PE3815	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	20 dB/100ft	44 W

12"	24"	36"	48"	60"	72"	Custom Len.
$125.99	$127.99	$127.99	$129.99	$129.99	$131.99	See Web

13

RG141A/U Coax, 50 Ohm

Part No. PE34428	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.19" dia.	13 dB/100ft	650 W

12"	24"	36"	48"	60"	72"	Custom Len.
$151.99	$151.99	$167.99	$165.99	$185.99	$193.99	See Web

14

RG142B/U Coax, 50 Ohm

Part No. PE3843	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	13 dB/100ft	650 W

12"	24"	36"	48"	60"	72"	Custom Len.
$119.99	$119.99	$133.99	$131.99	$147.99	$155.99	See Web

15

Part No. PE3W03503	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	12.9 dB/100ft	600 W

12"	24"	36"	48"	60"	50CM	Custom Len.
$86.99	$94.99	$101.99	$109.99	$115.99	$91.99	See Web

16

RG174A/U Coax, 50 Ohm

Part No. PE33706	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.1" dia.	32 dB/100ft	16 W

12"	24"	36"	48"	60"	72"	Custom Len.
$143.99	$145.99	$145.99	$147.99	$147.99	$147.99	See Web

17

RG188A/U Coax, 50 Ohm

Part No. PE34430	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.11" dia.	26 dB/100ft	160 W

12"	24"	36"	48"	60"	72"	Custom Len.
$145.99	$149.99	$143.99	$145.99	$147.99	$161.99	See Web

18

RG213/U Coax, 50 Ohm

Part No. PE35384	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.405" dia.	9 dB/100ft	190 W

12"	24"	36"	48"	60"	-	Custom Len.
$121.99	$123.99	$125.99	$127.99	$129.99	-	See Web

19

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

RG214/U Coax, 50 Ohm

Part No. PE3117				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	20
12"	24"	36"	48"	60"	72"	Custom Len.	
$137.99	$145.99	$155.99	$155.99	$175.99	$185.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3992				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	21
12"	24"	36"	48"	60"	72"	Custom Len.	
$113.99	$117.99	$121.99	$123.99	$121.99	$131.99	See Web	

RG225/U Coax, 50 Ohm

Part No. PE34421				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	22
12"	24"	36"	48"	60"	72"	Custom Len.	
$163.99	$207.99	$251.99	$273.99	$341.99	$355.99	See Web	

RG303/U Coax, 50 Ohm

Part No. PE3W00305				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.17" dia.		650 W	23
12"	24"	36"	48"	60"	50CM	Custom Len.	
$115.99	$121.99	$129.99	$137.99	$145.99	$119.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34432				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	24
12"	24"	36"	48"	60"	72"	Custom Len.	
$135.99	$139.99	$143.99	$145.99	$149.99	$163.99	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3338				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	25
12"	24"	36"	48"	60"	72"	Custom Len.	
$135.99	$163.99	$183.99	$205.99	$211.99	$231.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34424				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	26
12"	24"	36"	48"	60"	72"	Custom Len.	
$121.99	$129.99	$137.99	$155.99	$155.99	$163.99	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE39229				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	27
12"	24"	36"	48"	60"	-	Custom Len.	
$89.99	$95.99	$107.99	$117.99	$127.99	-	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3895				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	28
12"	24"	36"	48"	60"	72"	Custom Len.	
$113.99	$115.99	$115.99	$117.99	$119.99	$119.99	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE3857				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	29
12"	24"	36"	48"	60"	72"	Custom Len.	
$121.99	$123.99	$123.99	$125.99	$123.99	$129.99	See Web	

SHV PLUG TO SHV JACK BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE3W03078				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.		600 W	30
12"	24"	36"	48"	60"	50CM	Custom Len.	
$113.99	$113.99	$121.99	$127.99	$133.99	$111.99	See Web	

SHV JACK BULKHEAD TO SHV PLUG



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE33018				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	31
12"	24"	36"	48"	60"	-	Custom Len.	
$129.99	$131.99	$131.99	$133.99	$135.99	-	See Web	

SMA MALE TO 1.85MM MALE



Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE36541				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	32
6"	12"	18"	24"	36"	48"	Custom Len.	
$235.99	$235.99	$255.99	$247.99	$261.99	$273.99	See Web	

Standard Flexible Cable Assemblies

PE-P103 Coax, 50 Ohm

Part No. PE3C6633				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.103" dia.	29.48 dB/100ft		33
12"	36"	48"	200CM	-	-	Custom Len.	
$295.99	$359.99	$391.99	$473.99	-	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE36539					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22 dB/100ft	130 W	34
6"	12"	18"	24"	36"	48"	Custom Len.		
$243.99	$235.99	$239.99	$243.99	$251.99	$259.99	See Web		

SMA MALE TO 2.4MM MALE



Standard Flexible Cable Assemblies

PE-P103 Coax, 50 Ohm

Part No. PE3C6634				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.103" dia.	29.48 dB/100ft		35
24"	36"	48"	50CM	150CM	-	Custom Len.	
$291.99	$333.99	$365.99	$291.99	$395.99	-	See Web	

SMA MALE TO 2.92MM MALE



Standard Flexible Cable Assemblies

PE-P103 Coax, 50 Ohm

Part No. PE3C6632				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.103" dia.	29.48 dB/100ft		36
60"	100CM	150CM	200CM	-	-	Custom Len.	
$377.99	$335.99	$389.99	$425.99	-	-	See Web	

SMA MALE TO 7/16 DIN MALE



Low PIM Formable Cable Assemblies

PE-SR402FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2007						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						0.161" dia.			37
100CM	200CM	-	-	-	-	-	-	Custom Len.	
$135.99	$147.99	-	-	-	-	-	-	See Web	

Standard Formable Cable Assemblies

PE-SR401FL Coax, 50 Ohm

Part No. PE36169					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						7.6 dB/100ft	1,400 W	38
12"	24"	36"	48"	60"	72"	Custom Len.		
$269.99	$287.99	$305.99	$323.99	$341.99	$359.99	See Web		

PE-SR402FL Coax, 50 Ohm

Part No. PE36173				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	39
12"	24"	36"	48"	60"	72"	Custom Len.	
$213.99	$221.99	$229.99	$239.99	$247.99	$257.99	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE36157				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	40
12"	24"	36"	48"	60"	72"	Custom Len.	
$265.99	$267.99	$271.99	$275.99	$279.99	$281.99	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3221				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	41
12"	24"	36"	48"	60"	72"	Custom Len.	
$161.99	$163.99	$163.99	$165.99	$165.99	$167.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3224				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		42
12"	24"	36"	48"	60"	72"	Custom Len.	
$87.99	$94.99	$101.99	$107.99	$115.99	$119.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE36159				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	43
12"	24"	36"	48"	60"	72"	Custom Len.	
$259.99	$261.99	$263.99	$265.99	$267.99	$269.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3233				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	44
12"	24"	36"	48"	60"	72"	Custom Len.	
$261.99	$271.99	$279.99	$289.99	$297.99	$307.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

RG223/U Coax, 50 Ohm

Part No. PE36161				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W
12"	24"	36"	48"	60"	72"	Custom Len.
$84.99	$92.99	$91.99	$94.99	$98.99	$103.99	See Web

45

RG393/U Coax, 50 Ohm

Part No. PE36163				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W
12"	24"	36"	48"	60"	72"	Custom Len.
$275.99	$293.99	$313.99	$331.99	$351.99	$369.99	See Web

46

RG400/U Coax, 50 Ohm

Part No. PE36165				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W
12"	24"	36"	48"	60"	72"	Custom Len.
$205.99	$215.99	$223.99	$231.99	$239.99	$249.99	See Web

47

Standard Semi-Rigid Cable Assemblies

RG401/U Coax, 50 Ohm

Part No. PE36167				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W
12"	24"	36"	48"	60"	72"	Custom Len.
$281.99	$307.99	$333.99	$359.99	$385.99	Call	See Web

48

RG402/U Coax, 50 Ohm

Part No. PE36171				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W
12"	24"	36"	48"	60"	72"	Custom Len.
$215.99	$225.99	$233.99	$241.99	$251.99	$259.99	See Web

49

SMA MALE TO BNC MALE



Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3C0051				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
$42.19	$43.19	$43.99	$44.99	$45.99	-	See Web

50

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE34008				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W
12"	24"	36"	48"	60"	-	Custom Len.
$84.99	$94.99	$97.99	$107.99	$123.99	-	See Web

51

PE-SR405FL Coax, 50 Ohm

Part No. PE35109				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W
12"	24"	36"	48"	60"	-	Custom Len.
$85.99	$99.99	$115.99	$127.99	$141.99	-	See Web

52

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3615				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	72"	Custom Len.
$49.79	$50.99	$51.99	$52.99	$53.99	$54.99	See Web

53

RG142B/U Coax, 50 Ohm

Part No. PE3696				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W
12"	24"	36"	48"	60"	72"	Custom Len.
$48.99	$60.99	$67.99	$75.99	$83.99	$90.99	See Web

54

RG174A/U Coax, 50 Ohm

Part No. PE3C3328				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W
12"	24"	36"	48"	60"	72"	Custom Len.
$51.99	$52.99	$52.99	$53.99	$54.99	$55.99	See Web

55

RG178B/U Coax, 50 Ohm

Part No. PE33258				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W
12"	24"	36"	48"	60"	72"	Custom Len.
$81.99	$83.99	$84.99	$85.99	$81.99	$88.99	See Web

56

RG188A/U Coax, 50 Ohm

Part No. PE3C2035				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$52.99	$55.99	$58.99	$61.99	$60.99	$67.99	See Web

57

RG196A/U Coax, 50 Ohm

Part No. PE33523				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W
12"	24"	36"	48"	60"	72"	Custom Len.
$86.99	$88.99	$83.99	$85.99	$86.99	$88.99	See Web

58

RG213/U Coax, 50 Ohm

Part No. PE36661				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W
12"	24"	36"	48"	60"	-	Custom Len.
$141.99	$143.99	$145.99	$147.99	$149.99	-	See Web

59

RG214/U Coax, 50 Ohm

Part No. PE33519				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W
12"	24"	36"	48"	60"	72"	Custom Len.
$153.99	$163.99	$171.99	$181.99	$189.99	$199.99	See Web

60

RG223/U Coax, 50 Ohm

Part No. PE3562				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W
12"	24"	36"	48"	60"	72"	Custom Len.
$47.59	$51.99	$54.99	$58.99	$61.99	$64.99	See Web

61

RG316/U Coax, 50 Ohm

Part No. PE3C2360				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$47.39	$51.99	$55.99	$59.99	$62.99	$66.99	See Web

62

RG393/U Coax, 50 Ohm

Part No. PE33521				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W
12"	24"	36"	48"	60"	72"	Custom Len.
$165.99	$185.99	$203.99	$223.99	$243.99	$261.99	See Web

63

RG400/U Coax, 50 Ohm

Part No. PE3613				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W
12"	24"	36"	48"	60"	72"	Custom Len.
$62.99	$71.99	$80.99	$89.99	$99.99	$101.99	See Web

64

PE-P195 Coax, 50 Ohm

Part No. PE33989				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W
12"	24"	36"	48"	60"	-	Custom Len.
$61.99	$72.99	$84.99	$97.99	$109.99	-	See Web

65

LMR-240 Coax, 50 Ohm

Part No. PE3C1830				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$49.59	$48.79	$49.99	$51.99	$52.99	$48.39	See Web

66

RG55B/U Coax, 53 Ohm

Part No. PE3479				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W
12"	24"	36"	48"	60"	72"	Custom Len.
$46.59	$52.99	$55.99	$59.99	$62.99	$65.99	See Web

67

RG59B/U Coax, 75 Ohm

Part No. PE3539				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$64.99	$61.99	$63.99	$64.99	$65.99	$70.99	See Web

68

RG179B/U Coax, 75 Ohm

Part No. PE3C3321				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	29.15 dB/100ft	240 W
12"	24"	36"	48"	60"	72"	Custom Len.
$52.99	$51.99	$54.99	$57.99	$60.99	$63.99	See Web

69

SMA MALE TO BNC MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3C0040				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
$59.99	$60.99	$61.99	$61.99	$62.99	-	See Web

70

SMA MALE TO FAKRA PLUG



Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE39342A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
$40.39	$45.99	$42.19	$42.99	$43.99	-	See Web

71

Part No. PE39342B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
$40.39	$41.19	$42.19	$42.99	$43.99	-	See Web

72

Part No. PE39342C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
$44.39	$45.99	$47.59	$48.99	$50.99	-	See Web

73

Part No. PE39342D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
$41.79	$44.39	$46.99	$49.59	$52.99	-	See Web

74

For our complete selection of cable assemblies, please visit our website

Part No. PE39342H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		75
12"	24"	36"	48"	60"	-	Custom Len.	
$40.39	$41.19	$42.19	$42.99	$43.99	-	See Web	
Part No. PE39342I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		76
12"	24"	36"	48"	60"	-	Custom Len.	
$41.79	$44.39	$46.99	$49.59	$52.99	-	See Web	
Part No. PE39342K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		77
12"	24"	36"	48"	60"	-	Custom Len.	
$40.39	$41.19	$42.19	$42.99	$43.99	-	See Web	
Part No. PE39342Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		78
12"	24"	36"	48"	60"	-	Custom Len.	
$47.99	$49.79	$51.99	$53.99	$55.99	-	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE39197C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	79
12"	24"	36"	48"	60"	-	Custom Len.	
$54.99	$51.99	$51.99	$52.99	$52.99	-	See Web	
Part No. PE39197D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	80
12"	24"	36"	48"	60"	-	Custom Len.	
$54.99	$51.99	$51.99	$52.99	$52.99	-	See Web	
Part No. PE39197H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	81
12"	24"	36"	48"	60"	-	Custom Len.	
$46.19	$46.79	$47.39	$47.99	$48.79	-	See Web	
Part No. PE39197I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	82
12"	24"	36"	48"	60"	-	Custom Len.	
$46.19	$46.79	$47.39	$47.99	$48.79	-	See Web	
Part No. PE39197K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	83
12"	24"	36"	48"	60"	-	Custom Len.	
$50.99	$51.99	$51.99	$52.99	$52.99	-	See Web	
Part No. PE39197Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	84
12"	24"	36"	48"	60"	-	Custom Len.	
$55.99	$56.99	$51.99	$52.99	$52.99	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE39343A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	85
12"	24"	36"	48"	60"	-	Custom Len.	
$53.99	$57.99	$60.99	$63.99	$67.99	-	See Web	
Part No. PE39343C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	86
12"	24"	36"	48"	60"	-	Custom Len.	
$58.99	$57.99	$60.99	$63.99	$67.99	-	See Web	
Part No. PE39343D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	87
12"	24"	36"	48"	60"	-	Custom Len.	
$58.99	$56.99	$60.99	$63.99	$66.99	-	See Web	
Part No. PE39343H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	88
12"	24"	36"	48"	60"	-	Custom Len.	
$48.79	$52.99	$55.99	$59.99	$62.99	-	See Web	
Part No. PE39343I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	89
12"	24"	36"	48"	60"	-	Custom Len.	
$48.79	$52.99	$55.99	$59.99	$62.99	-	See Web	
Part No. PE39343K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	90
12"	24"	36"	48"	60"	-	Custom Len.	
$48.79	$52.99	$55.99	$59.99	$62.99	-	See Web	
Part No. PE39343Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	91
12"	24"	36"	48"	60"	-	Custom Len.	
$58.99	$57.99	$60.99	$63.99	$67.99	-	See Web	

SMA MALE TO FAKRA JACK



Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE39347A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		92
12"	24"	36"	48"	60"	-	Custom Len.	
$45.99	$47.39	$53.99	$50.99	$52.99	-	See Web	

Part No. PE39347B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		93
12"	24"	36"	48"	60"	-	Custom Len.	
$44.39	$45.99	$47.59	$48.99	$50.99	-	See Web	
Part No. PE39347C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		94
12"	24"	36"	48"	60"	-	Custom Len.	
$45.99	$47.39	$53.99	$50.99	$52.99	-	See Web	
Part No. PE39347D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		95
12"	24"	36"	48"	60"	-	Custom Len.	
$41.79	$44.39	$46.99	$49.59	$52.99	-	See Web	
Part No. PE39347H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		96
12"	24"	36"	48"	60"	-	Custom Len.	
$40.39	$41.19	$42.19	$42.99	$43.99	-	See Web	
Part No. PE39347I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		97
12"	24"	36"	48"	60"	-	Custom Len.	
$40.39	$41.19	$42.19	$42.99	$43.99	-	See Web	
Part No. PE39347K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		98
12"	24"	36"	48"	60"	-	Custom Len.	
$41.79	$44.39	$46.99	$49.59	$52.99	-	See Web	
Part No. PE39347Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		99
12"	24"	36"	48"	60"	-	Custom Len.	
$46.99	$48.79	$50.99	$48.19	$49.79	-	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE39199A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	1
12"	24"	36"	48"	60"	-	Custom Len.	
$54.99	$51.99	$51.99	$52.99	$52.99	-	See Web	
Part No. PE39199B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	2
12"	24"	36"	48"	60"	-	Custom Len.	
$50.99	$51.99	$51.99	$52.99	$52.99	-	See Web	
Part No. PE39199C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	3
12"	24"	36"	48"	60"	-	Custom Len.	
$55.99	$51.99	$51.99	$57.99	$52.99	-	See Web	
Part No. PE39199D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	4
12"	24"	36"	48"	60"	-	Custom Len.	
$50.99	$55.99	$51.99	$56.99	$52.99	-	See Web	
Part No. PE39199H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	5
12"	24"	36"	48"	60"	-	Custom Len.	
$50.99	$56.99	$51.99	$52.99	$52.99	-	See Web	
Part No. PE39199I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	6
12"	24"	36"	48"	60"	-	Custom Len.	
$46.19	$46.79	$47.39	$47.99	$48.79	-	See Web	
Part No. PE39199K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	7
12"	24"	36"	48"	60"	-	Custom Len.	
$50.99	$51.99	$51.99	$52.99	$52.99	-	See Web	
Part No. PE39199Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	8
12"	24"	36"	48"	60"	-	Custom Len.	
$54.99	$55.99	$56.99	$56.99	$57.99	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE39348A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	9
12"	24"	36"	48"	60"	-	Custom Len.	
$53.99	$57.99	$60.99	$63.99	$67.99	-	See Web	
Part No. PE39348B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	10
12"	24"	36"	48"	60"	-	Custom Len.	
$53.99	$57.99	$60.99	$63.99	$67.99	-	See Web	
Part No. PE39348C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	11
12"	24"	36"	48"	60"	-	Custom Len.	
$57.99	$61.99	$60.99	$63.99	$73.99	-	See Web	
Part No. PE39348D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	12
12"	24"	36"	48"	60"	-	Custom Len.	
$48.79	$52.99	$55.99	$59.99	$62.99	-	See Web	
Part No. PE39348H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	13
12"	24"	36"	48"	60"	-	Custom Len.	
$53.99	$57.99	$60.99	$63.99	$74.99	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

***Coax Performance at 1 GHz** **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

Part No. PE39348I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	14
12"	24"	36"	48"	60"	-	Custom Len.	
$48.79	$52.99	$55.99	$59.99	$62.99	-	See Web	

Part No. PE39348K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	15
12"	24"	36"	48"	60"	-	Custom Len.	
$53.99	$62.99	$66.99	$63.99	$67.99	-	See Web	

Part No. PE39348Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	16
12"	24"	36"	48"	60"	-	Custom Len.	
$57.99	$57.99	$60.99	$69.99	$73.99	-	See Web	

SMA MALE TO MC-CARD PLUG



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36112				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	17
12"	24"	36"	48"	60"	72"	Custom Len.	
$51.99	$52.99	$52.99	$53.99	$53.99	$54.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36110				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	18
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.99	$61.99	$62.99	$63.99	$64.99	$66.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE36108				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	19
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.99	$58.99	$61.99	$65.99	$68.99	$72.99	See Web	

SMA MALE TO MINI UHF MALE



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3273				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	20
12"	24"	36"	48"	60"	72"	Custom Len.	
$48.39	$49.19	$50.99	$50.99	$51.99	$52.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3275				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		21
12"	24"	36"	48"	60"	72"	Custom Len.	
$48.19	$55.99	$61.99	$68.99	$76.99	$83.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3271				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	22
12"	24"	36"	48"	60"	72"	Custom Len.	
$49.99	$49.19	$52.99	$56.99	$59.99	$62.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3278				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	23
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.99	$62.99	$70.99	$79.99	$88.99	$96.99	See Web	

SMA MALE TO MMCX PLUG



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE34069				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	24
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.99	$67.99	$68.99	$68.99	$63.99	$64.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE34374				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	25
12"	24"	36"	48"	60"	72"	Custom Len.	
$75.99	$76.99	$72.99	$73.99	$74.99	$81.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34887				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	26
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.99	$72.99	$76.99	$79.99	$74.99	$77.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34122				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	27
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.99	$72.99	$76.99	$80.99	$77.99	$88.99	See Web	

SMA MALE TO MMCX PLUG RIGHT ANGLE



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39564				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	28
6"	9"	12"	18"	24"	-	Custom Len.	
$51.99	$48.79	$51.99	Call	$61.99	-	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE34777				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	29
12"	24"	36"	48"	60"	-	Custom Len.	
$81.99	$83.99	$84.99	$85.99	$87.99	-	See Web	

SMA MALE TO N MALE



Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38433				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		30
12"	24"	36"	48"	60"	-	Custom Len.	
$54.99	$57.99	$59.99	$64.99	$64.99	-	See Web	

PE-C195 Coax, 50 Ohm

Part No. PE35981				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	31
12"	24"	36"	48"	60"	-	Custom Len.	
$53.99	$54.99	$55.99	$56.99	$57.99	-	See Web	

PE-C200 Coax, 50 Ohm

Part No. PE36200				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10.8 dB/100ft	170 W	32
12"	24"	36"	48"	60"	-	Custom Len.	
$53.99	$57.99	$58.99	$65.99	$71.99	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE38645				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	33
12"	24"	36"	48"	60"	-	Custom Len.	
$67.99	$73.99	$74.99	$75.99	$77.99	-	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE3C0689				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		34
12"	24"	36"	48"	60"	50CM	Custom Len.	
$163.99	$185.99	$205.99	$225.99	$247.99	$177.99	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3C0044				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		35
12"	24"	36"	48"	60"	-	Custom Len.	
$67.99	$68.99	$69.99	$68.99	$69.99	-	See Web	

LMR-400 Coax, 50 Ohm

Part No. PE3W00832				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		36
12"	24"	36"	48"	60"	50CM	Custom Len.	
$76.99	$78.99	$79.99	$81.99	$83.99	$77.99	See Web	

LMR-240-UF Coax, 50 Ohm

Part No. PE3W01626				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.							37
12"	24"	36"	48"	60"	50CM	Custom Len.	
$57.99	$58.99	$60.99	$62.99	$63.99	$58.99	See Web	

Precision Formable Cable Assemblies

PE-80TEST Coax, 50 Ohm

Part No. PE3TC0105				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			38
48"	72"	-	-	-	-	Custom Len.	
$525.00	$630.00	-	-	-	-	See Web	

PE-90TEST Coax, 50 Ohm

Part No. PE3TC0303				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.151" dia.			39
-	-	24"	48"	72"	-	Custom Len.	
-	-	$337.99	$431.99	$530.00	-	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34268				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	40
6"	12"	18"	24"	36"	48"	Custom Len.	
$103.99	$107.99	$111.99	$117.99	$123.99	$131.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

PE-SR401FL Coax, 50 Ohm

Part No. PE34263				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	41
6"	12"	18"	24"	36"	48"	Custom Len.	
$159.99	$169.99	$167.99	$177.99	$207.99	$215.99	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE3448				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	400 W	42
6"	12"	18"	24"	36"	48"	Custom Len.	
$84.99	$89.99	$94.99	$99.99	$103.99	$113.99	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3657				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	43
6"	12"	18"	24"	36"	48"	Custom Len.	
$101.99	$101.99	$107.99	$113.99	$125.99	$137.99	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3323				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	44
12"	24"	36"	48"	60"	72"	Custom Len.	
$163.99	$157.99	$171.99	$165.99	$169.99	$171.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3568				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	45
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.99	$67.99	$75.99	$83.99	$90.99	$98.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3291				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	46
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.99	$63.99	$62.99	$65.99	$65.99	$66.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3321				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	47
12"	24"	36"	48"	60"	72"	Custom Len.	
$88.99	$90.99	$91.99	$87.99	$88.99	$95.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3911				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	48
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.99	$71.99	$68.99	$71.99	$74.99	$77.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3422				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	49
12"	24"	36"	48"	60"	72"	Custom Len.	
$159.99	$167.99	$177.99	$185.99	$195.99	$217.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3519				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	50
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.99	$59.99	$62.99	$66.99	$70.99	$74.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3957				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	51
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.99	$56.99	$60.99	$63.99	$68.99	$72.99	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3302				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	52
12"	24"	36"	48"	60"	72"	Custom Len.	
$171.99	$191.99	$209.99	$243.99	$263.99	$285.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3614				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	53
12"	24"	36"	48"	60"	72"	Custom Len.	
$71.99	$81.99	$90.99	$99.99	$109.99	$119.99	See Web	

PE-P141 Coax, 50 Ohm

Part No. PE304				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			54
12"	24"	36"	48"	60"	72"	Custom Len.	
$191.99	$211.99	$225.99	$243.99	$253.99	$267.99	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE3318				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	55
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.99	$84.99	$96.99	$109.99	$121.99	$123.99	See Web	

PE-P142FLX Coax, 50 Ohm

Part No. PE3C0252				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.6 dB/100ft		56
12"	24"	36"	48"	60"	300"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

LMR-240-DB Coax, 50 Ohm

Part No. PE3C3354				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	7.66 dB/100ft		57
12"	50CM	24"	36"	100CM	48"	Custom Len.	
$51.99	$49.79	$50.99	$51.99	$52.99	$53.99	See Web	

LMR-195 Coax, 50 Ohm

Part No. PE3C0121				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		58
12"	24"	36"	48"	60"	-	Custom Len.	
$57.99	$58.99	$59.99	$60.99	$61.99	-	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3C0102				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		59
12"	24"	36"	48"	60"	-	Custom Len.	
$51.99	$52.99	$53.99	$54.99	$56.99	-	See Web	

LMR-240-UF Coax, 50 Ohm

Part No. PE3CA1067				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft		60
12"	24"	36"	48"	60"	72"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE34257				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	61
6"	12"	18"	24"	36"	48"	Custom Len.	
$105.99	$111.99	$117.99	$121.99	$143.99	$145.99	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE34261				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	62
6"	12"	18"	24"	36"	48"	Custom Len.	
$105.99	$109.99	$115.99	$121.99	$129.99	$139.99	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34259				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	63
6"	12"	18"	24"	36"	48"	Custom Len.	
$143.99	$163.99	$177.99	$191.99	$195.99	$217.99	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34265				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	64
6"	12"	18"	24"	36"	48"	Custom Len.	
$85.99	$90.99	$96.99	$96.99	$109.99	$119.99	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34270				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	65
6"	12"	18"	24"	36"	48"	Custom Len.	
$98.99	$98.99	$103.99	$109.99	$119.99	$129.99	See Web	

RG401/U Coax, 50 Ohm

Part No. PE33001				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	1,400 W	66
6"	12"	18"	24"	36"	48"	Custom Len.	
$167.99	$169.99	$183.99	$197.99	$223.99	$251.99	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3828				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	67
6"	12"	18"	24"	36"	48"	Custom Len.	
$99.99	$103.99	$103.99	$107.99	$123.99	$121.99	See Web	

Standard Flexible Cable Assemblies

RG55B/U Coax, 53 Ohm

Part No. PE3654				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	68
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.99	$59.99	$66.99	$64.99	$67.99	$70.99	See Web	

SMA MALE TO
N MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C1037				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		69
12"	24"	36"	48"	60"	50CM	Custom Len.	
$287.99	$307.99	$329.99	$349.99	$369.99	$301.99	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3236				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		70
12"	24"	36"	48"	60"	50CM	Custom Len.	
$297.99	$329.99	$361.99	$393.99	$425.99	$319.99	See Web	

Part No. PE3C3251				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		71
12"	24"	36"	48"	60"	50CM	Custom Len.	
$471.99	$505.00	$540.00	$570.00	$605.00	$493.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

For our complete selection of cable assemblies, please visit our website

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE3W00507				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$74.99	$84.99	$93.99	$103.99	$113.99	$80.99	See Web

72

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3W00504				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.161" dia.		450 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$74.99	$84.99	$94.99	$105.99	$115.99	$80.99	See Web

73

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3076				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	-	Custom Len.
$76.99	$77.99	$78.99	$80.99	$81.99	-	See Web

74

Part No. PE3W08374				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
36"	50CM	-	-	-	-	Custom Len.
$69.99	$68.99	-	-	-	-	See Web

75

SMA MALE TO N FEMALE



Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3W00177				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$44.39	$62.99	$62.99	$63.99	$64.99	$62.99	See Web

76

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3237				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$277.99	$311.99	$343.99	$375.99	$407.99	$299.99	See Web

77

Part No. PE3C3252				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$301.99	$333.99	$365.99	$397.99	$431.99	$323.99	See Web

78

Standard Flexible Cable Assemblies

PE-P195 Coax, 50 Ohm

Part No. PE3W00250				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$75.99	$86.99	$98.99	$109.99	$121.99	$70.99	See Web

79

SMA MALE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C2162				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$229.99	$251.99	$271.99	$291.99	$313.99	$243.99	See Web

80

Precision Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39455				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W
3"	6"	9"	12"	18"	24"	Custom Len.
Call	$80.99	$72.99	$80.99	$85.99	$90.99	See Web

81

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39469				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W
6"	9"	12"	18"	-	-	Custom Len.
$66.99	Call	$66.99	$72.99	-	-	See Web

82

PE-SR405FL Coax, 50 Ohm

Part No. PE39447				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W
6"	9"	12"	18"	24"	-	Custom Len.
$32.99	$56.99	$32.99	Call	Call	-	See Web

83

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39461				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W
6"	9"	12"	18"	24"	-	Custom Len.
$62.99	$62.99	Call	$68.99	$73.99	-	See Web

84

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3246				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$375.99	$407.99	$439.99	$471.99	$505.00	$395.99	See Web

85

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34153				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W
6"	12"	18"	24"	36"	48"	Custom Len.
$115.99	$119.99	$121.99	$125.99	$135.99	$143.99	See Web

86

PE-SR401FL Coax, 50 Ohm

Part No. PE34163				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W
6"	12"	18"	24"	36"	48"	Custom Len.
$137.99	$137.99	$147.99	$157.99	$175.99	$193.99	See Web

87

PE-SR402FL Coax, 50 Ohm

Part No. PE33996				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W
6"	12"	18"	24"	36"	48"	Custom Len.
$98.99	$98.99	$103.99	$109.99	$119.99	$127.99	See Web

88

PE-SR405FL Coax, 50 Ohm

Part No. PE33844				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W
6"	12"	18"	24"	36"	48"	Custom Len.
$99.99	$101.99	$107.99	$113.99	$125.99	$137.99	See Web

89

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3013				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
6"	12"	18"	24"	36"	48"	Custom Len.
$71.99	$73.99	$71.99	$74.99	$75.99	$77.99	See Web

90

RG142B/U Coax, 50 Ohm

Part No. PE3345				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W
6"	12"	18"	24"	36"	48"	Custom Len.
$63.99	$63.99	$71.99	$74.99	$82.99	$90.99	See Web

91

RG174A/U Coax, 50 Ohm

Part No. PE34171				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W
6"	12"	18"	24"	36"	48"	Custom Len.
$81.99	$82.99	$76.99	$76.99	$77.99	$77.99	See Web

92

RG178B/U Coax, 50 Ohm

Part No. PE34174				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W
6"	12"	18"	24"	36"	48"	Custom Len.
$78.99	$79.99	$80.99	$80.99	$81.99	$83.99	See Web

93

RG188A/U Coax, 50 Ohm

Part No. PE34176				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W
6"	12"	18"	24"	36"	48"	Custom Len.
$70.99	$71.99	$73.99	$74.99	$77.99	$79.99	See Web

94

RG213/U Coax, 50 Ohm

Part No. PE34185				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W
6"	12"	18"	24"	36"	48"	Custom Len.
$155.99	$157.99	$157.99	$159.99	$161.99	$163.99	See Web

95

RG214/U Coax, 50 Ohm

Part No. PE33481				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W
6"	12"	18"	24"	36"	48"	Custom Len.
$155.99	$155.99	$169.99	$163.99	$173.99	$181.99	See Web

96

RG223/U Coax, 50 Ohm

Part No. PE3193				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W
6"	12"	18"	24"	36"	48"	Custom Len.
$64.99	$66.99	$62.99	$64.99	$68.99	$71.99	See Web

97

RG316/U Coax, 50 Ohm

Part No. PE33555				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
6"	12"	18"	24"	36"	48"	Custom Len.
$81.99	$83.99	$79.99	$80.99	$91.99	$95.99	See Web

98

RG316-DS Coax, 50 Ohm

Part No. PE33929				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W
6"	12"	18"	24"	36"	48"	Custom Len.
$73.99	$79.99	$75.99	$83.99	$87.99	$84.99	See Web

99

RG393/U Coax, 50 Ohm

Part No. PE34183				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W
6"	12"	18"	24"	36"	48"	Custom Len.
$147.99	$157.99	$167.99	$177.99	$195.99	$215.99	See Web

1

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

RG400/U Coax, 50 Ohm

Part No. PE33117				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W
6"	12"	18"	24"	36"	48"	Custom Len.
$73.99	$77.99	$77.99	$86.99	$95.99	$105.99	See Web

2

PE-P195 Coax, 50 Ohm

Part No. PE34178				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W
6"	12"	18"	24"	36"	48"	Custom Len.
$78.99	$84.99	$83.99	$89.99	$101.99	$111.99	See Web

3

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE34148				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.047" dia.	40 dB/100ft	32 W
6"	12"	18"	24"	36"	48"	Custom Len.
$115.99	$121.99	$127.99	$133.99	$145.99	$157.99	See Web

4

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34159				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W
6"	12"	18"	24"	36"	48"	Custom Len.
$123.99	$133.99	$143.99	$155.99	$175.99	$197.99	See Web

5

PE-SR047AL Coax, 50 Ohm

Part No. PE34151				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W
6"	12"	18"	24"	36"	48"	Custom Len.
$115.99	$119.99	$125.99	$129.99	$141.99	$151.99	See Web

6

PE-SR402AL Coax, 50 Ohm

Part No. PE34143				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W
6"	12"	18"	24"	36"	48"	Custom Len.
$96.99	$103.99	$109.99	$115.99	$119.99	$139.99	See Web

7

PE-SR405AL Coax, 50 Ohm

Part No. PE34155				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W
6"	12"	18"	24"	36"	48"	Custom Len.
$95.99	$95.99	$101.99	$107.99	$127.99	$125.99	See Web

8

RG401/U Coax, 50 Ohm

Part No. PE34157				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W
6"	12"	18"	24"	36"	48"	Custom Len.
$149.99	$149.99	$163.99	$175.99	$203.99	$229.99	See Web

9

RG402/U Coax, 50 Ohm

Part No. PE3769				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W
6"	12"	18"	24"	36"	48"	Custom Len.
$95.99	$101.99	$101.99	$105.99	$115.99	$121.99	See Web

10

RG405/U Coax, 50 Ohm

Part No. PE3367				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W
6"	12"	18"	24"	36"	48"	Custom Len.
$85.99	$89.99	$94.99	$98.99	$107.99	$115.99	See Web

11

Standard Flexible Cable Assemblies

RG55B/U Coax, 53 Ohm

Part No. PE34169				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W
6"	12"	18"	24"	36"	48"	Custom Len.
$62.99	$62.99	$63.99	$64.99	$67.99	$70.99	See Web

12

SMA MALE TO
NMO MOUNT SEXLESS



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37840				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
60"	120"	180"	-	-	-	Custom Len.
$63.99	$62.99	$73.99	-	-	-	See Web

13

SMA MALE TO
QMA MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38116				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W
12"	24"	36"	48"	60"	72"	Custom Len.
$57.99	$63.99	$59.99	$60.99	$61.99	$62.99	See Web

14

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE38275				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	72"	Custom Len.
$67.99	$62.99	$63.99	$64.99	$65.99	$66.99	See Web

15

RG316/U Coax, 50 Ohm

Part No. PE38273				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$67.99	$70.99	$74.99	$82.99	$81.99	$85.99	See Web

16

RG316-DS Coax, 50 Ohm

Part No. PE38274				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$89.99	$87.99	$91.99	$94.99	$98.99	$103.99	See Web

17

SMA MALE TO
SMA MALE



Standard Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C0057				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
$60.99	$61.99	$62.99	$63.99	$64.99	-	See Web

18

Part No. PE3C0113				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
$56.99	$57.99	$58.99	$59.99	$60.99	-	See Web

19

LMR-195 Coax, 50 Ohm

Part No. PE3C0038				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
$45.99	$46.79	$47.79	$48.79	$49.79	-	See Web

20

Part No. PE3C3055				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
Call	Call	Call	Call	Call	-	See Web

21

PE-P160LL Coax, 50 Ohm

Part No. PE3C5241				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.	11 dB/100ft	560 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$263.99	$289.99	$315.99	$341.99	$367.99	$279.99	See Web

22

Low PIM Flexible Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5888				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$71.99	$78.99	$85.99	$92.99	$99.99	$75.99	See Web

23

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE37908				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
$62.99	$63.99	$65.99	$67.99	$69.99	-	See Web

24

PE-C195 Coax, 50 Ohm

Part No. PE35784				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W
12"	24"	36"	48"	60"	-	Custom Len.
$51.99	$52.99	$53.99	$54.99	$55.99	-	See Web

25

PE-C240 Coax, 50 Ohm

Part No. PE38628				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W
12"	24"	36"	48"	60"	-	Custom Len.
$65.99	$69.99	$70.99	$73.99	$77.99	-	See Web

26

PE-P142LL Coax, 50 Ohm

Part No. PE3C0230				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.32" dia.	7.2 dB/100ft	
12"	24"	36"	48"	60"	72"	Custom Len.
$345.99	$369.99	$425.99	$467.99	$580.00	$595.00	See Web

27

LMR-240-DB Coax, 50 Ohm

Part No. PE3W03353				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.24" dia.	7.66 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$66.99	$67.99	$68.99	$70.99	$71.99	$66.99	See Web

28

LMR-240 Coax, 50 Ohm

Part No. PE3C0052				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
$63.99	$64.99	$66.99	$67.99	$68.99	-	See Web

29

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

For our complete selection of cable assemblies, please visit our website

Part No. PE3C0103				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		30
12"	24"	36"	48"	60"	-	Custom Len.	
$48.59	$49.79	$51.99	$52.99	$53.99	-	See Web	

LMR-400-DB Coax, 50 Ohm

Part No. PE3W01582				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.15 dB/100ft		31
12"	24"	36"	48"	60"	50CM	Custom Len.	
$89.99	$91.99	$92.99	$94.99	$96.99	$90.99	See Web	

Precision Formable Cable Assemblies

PE-80TEST Coax, 50 Ohm

Part No. PE3TC0101				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			32
24"	48"	72"	-	-	-	Custom Len.	
$393.99	$499.99	$610.00	-	-	-	See Web	

Part No. PE3TC0201				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			33
24"	48"	72"	120"	-	-	Custom Len.	
$570.00	$680.00	$785.00	Call	-	-	See Web	

PE-90TEST Coax, 50 Ohm

Part No. PE3TC0301				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.151" dia.			34
24"	48"	72"	144"	-	-	Custom Len.	
$289.99	$411.99	$510.00	Call	-	-	See Web	

Part No. PE3TC0401				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.151" dia.			35
24"	48"	72"	-	-	-	Custom Len.	
$493.99	$595.00	$690.00	-	-	-	See Web	

Precision Flexible Cable Assemblies

PE-P141 Coax, 50 Ohm

Part No. PE312				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			36
12"	24"	36"	48"	60"	72"	Custom Len.	
$195.99	$201.99	$199.99	$181.99	Call	Call	See Web	

Part No. PE3CA1130					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.163" dia.			37
12"	18"	24"	36"	48"	60"	Custom Len.		
$163.99	Call	$169.99	$183.99	$181.99	$209.99	See Web		

Low PIM Formable Cable Assemblies

PE-SR402FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2008				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.			38
12"	30"	40"	60"	70"	75"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

Low PIM Flexible Cable Assemblies

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8008				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			39
12"	24"	36"	48"	60"	50CM	Custom Len.	
$41.19	$43.59	$46.19	$48.59	$51.99	$40.19	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6207				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	40
12"	24"	36"	48"	60"	50CM	Custom Len.	
$53.99	$60.99	$67.99	$74.99	$81.99	$58.99	See Web	

Test Flexible Cable Assemblies

PE-P160 Coax, 50 Ohm

Part No. PE366				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.	12.62 dB/100ft		41
12"	24"	36"	48"	60"	50CM	Custom Len.	
Call	Call	$401.99	$431.99	Call	Call	See Web	

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA1801				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			42
24"	400"	-	-	-	-	Custom Len.	
$975.00	Call	-	-	-	-	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE341				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		43
12"	24"	36"	48"	60"	46CM	Custom Len.	
$143.99	$163.99	$185.99	$205.99	$225.99	Call	See Web	

PE-P300LL Coax, 50 Ohm

Part No. PE333				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	4.6 dB/100ft		44
12"	24"	36"	48"	60"	50CM	Custom Len.	
$311.99	$345.99	$377.99	$411.99	$443.99	$333.99	See Web	

Part No. PE336				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			45
12"	24"	36"	48"	60"	72"	Custom Len.	
$301.99	$333.99	$367.99	$407.99	$433.99	$481.99	See Web	

Part No. PE3C3235				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		46
12"	24"	36"	48"	60"	50CM	Custom Len.	
$197.99	$229.99	$261.99	$293.99	$325.99	$217.99	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34186					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.047" dia.	36 dB/100ft	32 W	47
6"	12"	18"	24"	36"	48"	Custom Len.		
$107.99	$113.99	$117.99	$115.99	$123.99	$131.99	See Web		

PE-SR401FL Coax, 50 Ohm

Part No. PE34188					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						6.8 dB/100ft	279 W	48
6"	12"	18"	24"	36"	48"	Custom Len.		
$147.99	$155.99	$165.99	$175.99	$215.99	$233.99	See Web		

PE-SR402FL Coax, 50 Ohm

Part No. PE3481					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						12 dB/100ft	400 W	49
6"	12"	18"	24"	36"	48"	Custom Len.		
$53.99	$58.99	$63.99	$67.99	$77.99	$88.99	See Web		

Part No. PE39423					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						12 dB/100ft	400 W	50
3"	6"	9"	12"	18"	24"	Custom Len.		
$57.99	$56.99	$53.99	$56.99	$62.99	$69.99	See Web		

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39437					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.161" dia.	11.89 dB/100ft	303.4 W	51
6"	9"	12"	18"	24"	-	Custom Len.		
$71.99	$68.99	$71.99	$76.99	$82.99	-	See Web		

PE-SR405FL Coax, 50 Ohm

Part No. PE3867					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22.5 dB/100ft	105 W	52
6"	12"	18"	24"	36"	48"	Custom Len.		
$61.99	$68.99	$75.99	$82.99	$90.99	$103.99	See Web		

Part No. PE39415					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22.5 dB/100ft	105 W	53
6"	9"	12"	18"	24"	-	Custom Len.		
$61.99	$59.99	$61.99	$68.99	$74.99	-	See Web		

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39429					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.105" dia.	19.5 dB/100ft	121.5 W	54
6"	9"	12"	18"	24"	-	Custom Len.		
$61.99	$61.99	$61.99	$66.99	$72.99	-	See Web		

Standard Flexible Cable Assemblies

RG8X Coax, 50 Ohm

Part No. PE39087				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13.5 dB/100ft	60 W	55
12"	24"	36"	48"	60"	-	Custom Len.	
$80.99	$84.99	$93.99	$98.99	$103.99	-	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3369					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.195" dia.	20 dB/100ft	44 W	56
6"	12"	18"	24"	36"	48"	Custom Len.		
$53.99	$56.99	$54.99	$54.99	$55.99	$56.99	See Web		

Part No. PE36689					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.195" dia.	20 dB/100ft	44 W	57
24"	36"	48"	-	-	-	Custom Len.		
$137.99	$131.99	$139.99	-	-	-	See Web		

Part No. PE36690					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.195" dia.	20 dB/100ft	80 W	58
24"	36"	48"	72"	-	-	Custom Len.		
$165.99	$165.99	$167.99	$169.99	-	-	See Web		

RG142B/U Coax, 50 Ohm

Part No. PE3385					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.195" dia.	13 dB/100ft	600 W	59
6"	12"	18"	24"	36"	48"	Custom Len.		
$61.99	$65.99	$68.99	$72.99	$80.99	$88.99	See Web		

RG174A/U Coax, 50 Ohm

Part No. PE3353					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.1" dia.	32 dB/100ft	16 W	60
6"	12"	18"	24"	36"	48"	Custom Len.		
$61.99	$62.99	$62.99	$62.99	$63.99	$63.99	See Web		

Part No. PE3W00365					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.11" dia.	32 dB/100ft	17 W	61
12"	24"	36"	48"	60"	50CM	Custom Len.		
$79.99	$79.99	$80.99	$81.99	$77.99	$75.99	See Web		

RG178B/U Coax, 50 Ohm

Part No. PE3574					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.072" dia.	44.4 dB/100ft	78 W	62
6"	12"	18"	24"	36"	48"	Custom Len.		
$80.99	$81.99	$82.99	$82.99	$84.99	$85.99	See Web		

See Our Website For Current Pricing & Real-Time Stock Availability!

For Custom Lengths, Metric Lengths or Special Configurations, Please call (949) 261-1920

For our complete selection of cable assemblies, please visit our website

RG188A/U Coax, 50 Ohm

Part No. PE3361	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.11" dia.	26 dB/100ft	160 W	63
6"	12"	18"	24"	36"	48"	Custom Len.
$61.99	$63.99	$64.99	$66.99	$69.99	$72.99	See Web

RG188-DS Coax, 50 Ohm

Part No. PE3778	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.122" dia.	30 dB/100ft	160 W	64
12"	24"	36"	48"	60"	-	Custom Len.
$67.99	$68.99	$76.99	$76.99	$85.99	-	See Web

RG213/U Coax, 50 Ohm

Part No. PE35571	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.405" dia.	8 dB/100ft	190 W	65
12"	24"	36"	48"	60"	-	Custom Len.
$207.99	$209.99	$211.99	$213.99	$215.99	-	See Web

RG214/U Coax, 50 Ohm

Part No. PE3121	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.425" dia.	7.32 dB/100ft	170 W	66
6"	12"	18"	24"	36"	48"	Custom Len.
$241.99	$241.99	$245.99	$249.99	$259.99	$267.99	See Web

RG223/U Coax, 50 Ohm

Part No. PE3377	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.21" dia.	13.4 dB/100ft	53 W	67
6"	12"	18"	24"	36"	48"	Custom Len.
$48.19	$48.19	$49.99	$51.99	$55.99	$58.99	See Web

Part No. PE3W02458	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.209" dia.	13.41 dB/100ft	50 W	68
12"	24"	36"	48"	60"	50CM	Custom Len.
$73.99	$90.99	$94.99	$98.99	$103.99	$89.99	See Web

RG316/U Coax, 50 Ohm

Part No. PE3573	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.102" dia.	38 dB/100ft	160 W	69
6"	12"	18"	24"	36"	48"	Custom Len.
$61.99	$63.99	$65.99	$66.99	$70.99	$74.99	See Web

RG316-DS Coax, 50 Ohm

Part No. PE3704	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.114" dia.	30 dB/100ft	160 W	70
12"	48CM	24"	36"	48"	60"	Custom Len.
$61.99	Call	$64.99	$68.99	$72.99	$76.99	See Web

RG400/U Coax, 50 Ohm

Part No. PE3500	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.195" dia.	14.7 dB/100ft	600 W	71
6"	12"	18"	24"	36"	48"	Custom Len.
$63.99	$68.99	$72.99	$77.99	$86.99	$96.99	See Web

PE-P086EAM Coax, 50 Ohm

Part No. PE3CA1039	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.104" dia.			72
12"	24"	36"	50CM	100CM	-	Custom Len.
$72.99	$88.99	$105.99	$94.99	$119.99	-	See Web

PE-P103 Coax, 50 Ohm

Part No. PE3C6631	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.103" dia.	29.48 dB/100ft		73
12"	24"	150CM	-	-	-	Custom Len.
$245.99	$275.99	$365.99	-	-	-	See Web

PE-P141 Coax, 50 Ohm

Part No. PE300	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.163" dia.	11.2 dB/100ft	600 W	74
12"	24"	36"	48"	60"	72"	Custom Len.
$141.99	$157.99	$173.99	$191.99	$207.99	$223.99	See Web

Part No. PE350	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.163" dia.	11.2 dB/100ft	600 W	75
12"	24"	36"	48"	60"	72"	Custom Len.
$113.99	$125.99	$143.99	$157.99	$163.99	$185.99	See Web

PE-P141FLX Coax, 50 Ohm

Part No. PE3CA1035	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.163" dia.			76
13CM	12"	24"	25"	36"	72"	Custom Len.
Call	$91.99	$117.99	Call	$131.99	Call	See Web

PE-P195 Coax, 50 Ohm

Part No. PE3138	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.195" dia.	12.5 dB/100ft	650 W	77
6"	12"	18"	24"	36"	48"	Custom Len.
$73.99	$73.99	$79.99	$86.99	$99.99	$113.99	See Web

Standard Semi-Rigid Cable Assemblies

PE-020SR Coax, 50 Ohm

Part No. PE34191	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.		85 dB/100ft	2.9 W	78
6"	12"	18"	24"	36"	48"	Custom Len.
$163.99	$173.99	$185.99	$197.99	$207.99	$229.99	See Web

PE-034SR Coax, 50 Ohm

Part No. PE34193	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.		60 dB/100ft	10 W	79
6"	12"	18"	24"	36"	48"	Custom Len.
$167.99	$165.99	$171.99	$189.99	$205.99	$209.99	See Web

PE-047SR Coax, 50 Ohm

Part No. PE3656	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.		40 dB/100ft	32 W	80
6"	12"	18"	24"	36"	48"	Custom Len.
$107.99	$115.99	$121.99	$127.99	$133.99	$157.99	See Web

PE-SR047AL Coax, 50 Ohm

Part No. PE3387	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.047" dia.	41 dB/100ft	32 W	81
6"	12"	18"	24"	36"	48"	Custom Len.
$109.99	$115.99	$115.99	$119.99	$139.99	$139.99	See Web

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34184	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.25" dia.	8 dB/100ft	1,400 W	82
6"	12"	18"	24"	36"	48"	Custom Len.
$161.99	$169.99	$171.99	$183.99	$205.99	$225.99	See Web

PE-SR402AL Coax, 50 Ohm

Part No. PE34180	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.141" dia.	13 dB/100ft	450 W	83
6"	12"	18"	24"	36"	48"	Custom Len.
$62.99	$68.99	$74.99	$81.99	$93.99	$107.99	See Web

PE-SR402TN Coax, 50 Ohm

Part No. PE3C1015	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.		12 dB/100ft		84
12"	24"	36"	48"	60"	72"	Custom Len.
$62.99	$71.99	$71.99	$77.99	$84.99	$90.99	See Web

PE-SR405AL Coax, 50 Ohm

Part No. PE34182	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.		23 dB/100ft	130 W	85
6"	12"	18"	24"	36"	48"	Custom Len.
$59.99	$64.99	$70.99	$76.99	$87.99	$93.99	See Web

RG401/U Coax, 50 Ohm

Part No. PE33003	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.		7.5 dB/100ft	1,400 W	86
6"	12"	18"	24"	36"	48"	Custom Len.
$165.99	$179.99	$193.99	$195.99	$233.99	$263.99	See Web

RG402/U Coax, 50 Ohm

Part No. PE3492	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.		12 dB/100ft	650 W	87
6"	12"	18"	24"	36"	48"	Custom Len.
$61.99	$66.99	$71.99	$76.99	$86.99	$96.99	See Web

RG405/U Coax, 50 Ohm

Part No. PE3818	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.		22 dB/100ft	130 W	88
6"	12"	18"	24"	36"	48"	Custom Len.
$59.99	$63.99	$68.99	$72.99	$81.99	$91.99	See Web

Standard Flexible Cable Assemblies

RG55B/U Coax, 53 Ohm

Part No. PE3572	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.202" dia.	16.5 dB/100ft	53 W	89
6"	12"	18"	24"	36"	48"	Custom Len.
$54.99	$57.99	$55.99	$60.99	$59.99	$62.99	See Web

RG59B/U Coax, 75 Ohm

Part No. PE3814	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.242" dia.	11.5 dB/100ft	77 W	90
6"	12"	18"	24"	36"	48"	Custom Len.
$83.99	$88.99	$83.99	$84.99	$85.99	$86.99	See Web

RG62A/U Coax, 93 Ohm

Part No. PE3899	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.242" dia.	13 dB/100ft	77 W	91
6"	12"	18"	24"	36"	48"	Custom Len.
$85.99	$85.99	$86.99	$86.99	$88.99	$90.99	See Web

RG179B/U Coax, 75 Ohm

Part No. PE3739	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.1" dia.	25 dB/100ft	200 W	92
6"	12"	18"	24"	36"	48"	Custom Len.
$58.99	$59.99	$60.99	$62.99	$65.99	$64.99	See Web

RG180B/U Coax, 95 Ohm

Part No. PE3245	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.141" dia.		250 W	93
12"	24"	36"	48"	60"	-	Custom Len.
$79.99	$79.99	$84.99	$95.99	$101.99	-	See Web

RG187A/U Coax, 75 Ohm

Part No. PE38059	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.11" dia.	25 dB/100ft	200 W	94
12"	24"	36"	48"	60"	-	Custom Len.
$61.99	$68.99	$68.99	$72.99	$76.99	-	See Web

SMA MALE TO
SMA MALE RIGHT ANGLE



Low PIM Flexible Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5894				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	95
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.99	$80.99	$125.99	$94.99	$101.99	$77.99	See Web	

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE36475				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	96
12"	24"	36"	48"	60"	-	Custom Len.	
$59.99	$60.99	$57.99	$58.99	$59.99	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE38624				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	97
12"	24"	36"	48"	60"	-	Custom Len.	
$85.99	$86.99	$83.99	$86.99	$90.99	-	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5246				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			98
12"	24"	36"	48"	60"	50CM	Custom Len.	
$309.99	$335.99	$363.99	$389.99	$415.99	$327.99	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3C0104				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		99
12"	24"	36"	48"	60"	-	Custom Len.	
$52.99	$51.99	$52.99	$55.99	$57.99	-	See Web	

Precision Flexible Cable Assemblies

PE-P141 Coax, 50 Ohm

Part No. PE351				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			1
6"	12"	24"	36"	48"	60"	Custom Len.	
$203.99	$209.99	$215.99	$237.99	$253.99	$267.99	See Web	

Part No. PE3C0806				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.	11.2 dB/100ft	550 W	2
12"	24"	36"	48"	60"	72"	Custom Len.	
$173.99	$187.99	$201.99	$215.99	$229.99	$243.99	See Web	

Low PIM Flexible Cable Assemblies

TFT-402 Coax, 50 Ohm

Part No. PE3C7977				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			3
12"	24"	36"	48"	60"	50CM	Custom Len.	
$50.99	$54.99	$59.99	$63.99	$67.99	$48.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8009				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			4
12"	24"	36"	48"	60"	50CM	Custom Len.	
$46.19	$48.79	$51.99	$53.99	$55.99	$45.39	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7864				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		5
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$62.99	$66.99	$70.99	$74.99	$60.99	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6210				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	6
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$64.99	$71.99	$78.99	$84.99	$62.99	See Web	

Test Flexible Cable Assemblies

PE-P160 Coax, 50 Ohm

Part No. PE367				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.	12.62 dB/100ft		7
12"	24"	36"	48"	60"	50CM	Custom Len.	
Call	Call	$429.99	$461.99	Call	Call	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C1722				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		8
12"	24"	36"	48"	60"	50CM	Custom Len.	
$333.99	$367.99	$399.99	$433.99	$465.99	$355.99	See Web	

Part No. PE3C3248				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		9
12"	24"	36"	48"	60"	50CM	Custom Len.	
$425.99	$457.99	$489.99	$525.00	$555.00	$445.99	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34197				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	10
6"	12"	18"	24"	36"	48"	Custom Len.	
$145.99	$155.99	$149.99	$155.99	$163.99	$173.99	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34202				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					6.8 dB/100ft	279 W	11
6"	12"	18"	24"	36"	48"	Custom Len.	
$175.99	$175.99	$185.99	$195.99	$211.99	$231.99	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE3483				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	400 W	12
6"	12"	18"	24"	36"	48"	Custom Len.	
$69.99	$74.99	$79.99	$83.99	$93.99	$107.99	See Web	

Part No. PE39425				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	400 W	13
6"	9"	12"	18"	24"	-	Custom Len.	
$53.99	$50.99	$53.99	$58.99	$63.99	-	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39439				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	14
6"	9"	12"	18"	24"	-	Custom Len.	
$63.99	$58.99	$63.99	$68.99	$73.99	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE39417				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	15
6"	9"	12"	18"	24"	-	Custom Len.	
$60.99	$57.99	$60.99	$66.99	$73.99	-	See Web	

Part No. PE3958				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	16
6"	12"	18"	24"	36"	48"	Custom Len.	
$89.99	$90.99	$97.99	$103.99	$117.99	$129.99	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W02993				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	121.5 W	17
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$69.99	$80.99	$91.99	$103.99	$66.99	See Web	

Part No. PE3W03751				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	121.5 W	18
12"	24"	36"	48"	60"	50CM	Custom Len.	
$80.99	$91.99	$103.99	$113.99	$123.99	$87.99	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3319				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	19
6"	12"	18"	24"	36"	48"	Custom Len.	
$68.99	$69.99	$69.99	$70.99	$65.99	$66.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3512				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	20
6"	12"	18"	24"	36"	48"	Custom Len.	
$64.99	$68.99	$72.99	$76.99	$83.99	$84.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3420				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	21
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.99	$80.99	$81.99	$81.99	$82.99	$77.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3865				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	22
6"	12"	18"	24"	36"	48"	Custom Len.	
$99.99	$101.99	$93.99	$93.99	$95.99	$96.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3510				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	23
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.99	$82.99	$77.99	$79.99	$88.99	$91.99	See Web	

Part No. PE3W04442				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	24
12"	24"	36"	48"	60"	50CM	Custom Len.	
$67.99	$71.99	$74.99	$77.99	$80.99	$69.99	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE3779				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	25
6"	12"	18"	24"	36"	48"	Custom Len.	
$66.99	$68.99	$71.99	$73.99	$72.99	$76.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3429				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	26
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.99	$73.99	$75.99	$77.99	$80.99	$84.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3513				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	27
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.99	$82.99	$84.99	$82.99	$89.99	$94.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3344				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	28
6"	12"	18"	24"	36"	48"	Custom Len.	
$69.99	$69.99	$71.99	$73.99	$77.99	$80.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3003				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	29
6"	12"	18"	24"	36"	48"	Custom Len.	
$78.99	$83.99	$87.99	$92.99	$101.99	$111.99	See Web	

PE-P086EAM Coax, 50 Ohm

Part No. PE3CA1040				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.104" dia.			30
12"	24"	36"	50CM	-	-	Custom Len.	
$78.99	$93.99	$109.99	$87.99	-	-	See Web	

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1036				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			31
10"	11"	12"	16"	24"	36"	Custom Len.	
Call	Call	$90.99	Call	$115.99	$135.99	See Web	

Standard Semi-Rigid Cable Assemblies

PE-020SR Coax, 50 Ohm

Part No. PE34204				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					85 dB/100ft	2.9 W	32
6"	12"	18"	24"	36"	48"	Custom Len.	
$165.99	$193.99	$187.99	$197.99	$219.99	$239.99	See Web	

PE-034SR Coax, 50 Ohm

Part No. PE34206				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					60 dB/100ft	10 W	33
6"	12"	18"	24"	36"	48"	Custom Len.	
$159.99	$167.99	$175.99	$181.99	$197.99	$211.99	See Web	

PE-047SR Coax, 50 Ohm

Part No. PE3230				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	34
6"	12"	18"	24"	36"	48"	Custom Len.	
$149.99	$149.99	$155.99	$161.99	$173.99	$187.99	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE3393				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	35
6"	12"	18"	24"	36"	48"	Custom Len.	
$133.99	$139.99	$145.99	$149.99	$161.99	$171.99	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34200				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	36
6"	12"	18"	24"	36"	48"	Custom Len.	
$165.99	$167.99	$179.99	$189.99	$211.99	$231.99	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34195				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	37
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.99	$86.99	$87.99	$93.99	$105.99	$117.99	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34199				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	38
6"	12"	18"	24"	36"	48"	Custom Len.	
$78.99	$83.99	$88.99	$93.99	$103.99	$113.99	See Web	

RG401/U Coax, 50 Ohm

Part No. PE34220				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	39
6"	12"	18"	24"	36"	48"	Custom Len.	
$179.99	$193.99	$189.99	$201.99	$227.99	$255.99	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3821				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	40
6"	12"	18"	24"	36"	48"	Custom Len.	
$84.99	$88.99	$86.99	$91.99	$101.99	$109.99	See Web	

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE3137				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	41
6"	12"	18"	24"	36"	48"	Custom Len.	
$84.99	$85.99	$85.99	$86.99	$87.99	$88.99	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE3411				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	42
6"	12"	18"	24"	36"	48"	Custom Len.	
$86.99	$87.99	$88.99	$89.99	$90.99	$92.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE3459				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	43
6"	12"	18"	24"	36"	48"	Custom Len.	
$77.99	$77.99	$78.99	$80.99	$83.99	$86.99	See Web	

RG180B/U Coax, 95 Ohm

Part No. PE3352				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.145" dia.		250 W	44
6"	12"	18"	24"	36"	48"	Custom Len.	
$73.99	$76.99	$78.99	$81.99	$86.99	$90.99	See Web	

SMA MALE TO SMA FEMALE



Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE37995				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		45
12"	24"	36"	48"	60"	-	Custom Len.	
$67.99	$64.99	$65.99	$67.99	$74.99	-	See Web	

PE-C195 Coax, 50 Ohm

Part No. PE36201				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	46
12"	24"	36"	48"	60"	-	Custom Len.	
$60.99	$61.99	$59.99	$60.99	$61.99	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE38638				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	47
12"	24"	36"	48"	60"	-	Custom Len.	
$70.99	$71.99	$73.99	$76.99	$80.99	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE39148				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	48
12"	24"	36"	48"	60"	-	Custom Len.	
$119.99	$121.99	$123.99	$125.99	$125.99	-	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE340				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft	820 W	49
12"	24"	36"	48"	60"	50CM	Custom Len.	
$193.99	$213.99	$235.99	$255.99	$277.99	$207.99	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3W02466				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.			50
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.99	$62.99	$63.99	$65.99	$66.99	$62.99	See Web	

LMR-240-UF Coax, 50 Ohm

Part No. PE3W04971				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft		51
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$61.99	$63.99	$64.99	$66.99	$61.99	See Web	

Precision Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39426				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	52
6"	9"	12"	18"	24"	-	Custom Len.	
$49.79	$45.39	$49.79	$54.99	$59.99	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE39418				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	53
6"	9"	12"	18"	24"	-	Custom Len.	
$46.99	$49.79	$49.79	$56.99	$62.99	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39432				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	54
6"	9"	12"	18"	24"	-	Custom Len.	
$46.99	$44.19	$46.99	$52.99	$57.99	-	See Web	

PE-80TEST Coax, 50 Ohm

Part No. PE3TC0102				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			55
24"	48"	72"	-	-	-	Custom Len.	
$447.99	$555.00	$665.00	-	-	-	See Web	

Part No. PE3TC0202				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			56
24"	48"	72"	-	-	-	Custom Len.	
$695.00	$805.00	$910.00	-	-	-	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7865				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		57
12"	24"	36"	48"	60"	50CM	Custom Len.	
$55.99	$61.99	$65.99	$69.99	$74.99	$60.99	See Web	

Test Flexible Cable Assemblies

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA1802				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			58
24"	48"	-	-	-	-	Custom Len.	
$1,000.00	$1,120.00	-	-	-	-	See Web	

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

For our complete selection of cable assemblies, please visit our website

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34228				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	59
6"	12"	18"	24"	36"	48"	Custom Len.	
$117.99	$117.99	$131.99	$125.99	$133.99	$143.99	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34233				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	60
6"	12"	18"	24"	36"	48"	Custom Len.	
$141.99	$141.99	$149.99	$159.99	$177.99	$195.99	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE3443				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	61
6"	12"	18"	24"	36"	48"	Custom Len.	
$69.99	$74.99	$73.99	$78.99	$87.99	$96.99	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39440				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	62
6"	9"	12"	18"	24"	-	Custom Len.	
$48.39	Call	$48.39	Call	$59.99	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3651				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	63
6"	12"	18"	24"	36"	48"	Custom Len.	
$85.99	$85.99	$98.99	$105.99	$111.99	$123.99	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3078				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	64
6"	12"	18"	24"	36"	48"	Custom Len.	
$65.99	$70.99	$66.99	$66.99	$72.99	$68.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3611				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	65
6"	12"	18"	24"	36"	48"	Custom Len.	
$63.99	$67.99	$64.99	$68.99	$82.99	$82.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3715				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	66
6"	12"	18"	24"	36"	48"	Custom Len.	
$70.99	$70.99	$71.99	$67.99	$72.99	$73.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3056				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	67
6"	12"	18"	24"	36"	48"	Custom Len.	
$85.99	$81.99	$81.99	$87.99	$88.99	$84.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3706				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	68
6"	12"	18"	24"	36"	48"	Custom Len.	
$69.99	$69.99	$71.99	$72.99	$75.99	$78.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3697				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	69
6"	12"	18"	24"	36"	48"	Custom Len.	
$58.99	$60.99	$61.99	$63.99	$67.99	$67.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3832				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	70
6"	12"	18"	24"	36"	48"	Custom Len.	
$72.99	$74.99	$75.99	$77.99	$77.99	$85.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3171				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	71
6"	12"	18"	24"	36"	48"	Custom Len.	
$78.99	$73.99	$75.99	$83.99	$87.99	$84.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3864				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	72
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.99	$71.99	$75.99	$79.99	$88.99	$97.99	See Web	

PE-P141 Coax, 50 Ohm

Part No. PE3C1876				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.	11.2 dB/100ft	550 W	73
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.99	$81.99	$96.99	$111.99	$125.99	$76.99	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE3160				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	74
6"	12"	18"	24"	36"	48"	Custom Len.	
$78.99	$82.99	$83.99	$89.99	$101.99	$111.99	See Web	

Standard Semi-Rigid Cable Assemblies

PE-020SR Coax, 50 Ohm

Part No. PE34224				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					85 dB/100ft	2.9 W	75
6"	12"	18"	24"	36"	48"	Custom Len.	
$165.99	$175.99	$185.99	$195.99	$217.99	$239.99	See Web	

PE-034SR Coax, 50 Ohm

Part No. PE34226				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					60 dB/100ft	10 W	76
6"	12"	18"	24"	36"	48"	Custom Len.	
$177.99	$177.99	$185.99	$191.99	$207.99	$233.99	See Web	

PE-047SR Coax, 50 Ohm

Part No. PE3188				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	77
6"	12"	18"	24"	36"	48"	Custom Len.	
$119.99	$119.99	$125.99	$131.99	$143.99	$157.99	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE3253				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					41 dB/100ft	32 W	78
6"	12"	18"	24"	36"	48"	Custom Len.	
$113.99	$113.99	$117.99	$121.99	$133.99	$143.99	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34230				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	79
6"	12"	18"	24"	36"	48"	Custom Len.	
$125.99	$135.99	$147.99	$157.99	$177.99	$199.99	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34235				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	80
6"	12"	18"	24"	36"	48"	Custom Len.	
$69.99	$75.99	$81.99	$84.99	$95.99	$107.99	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34237				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	81
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.99	$76.99	$81.99	$86.99	$96.99	$107.99	See Web	

RG401/U Coax, 50 Ohm

Part No. PE33896				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	82
6"	12"	18"	24"	36"	48"	Custom Len.	
$151.99	$151.99	$175.99	$179.99	$205.99	$233.99	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3823				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	83
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.99	$71.99	$80.99	$80.99	$89.99	$105.99	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3824				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	84
6"	12"	18"	24"	36"	48"	Custom Len.	
$83.99	$81.99	$86.99	$90.99	$98.99	$107.99	See Web	

Standard Flexible Cable Assemblies

RG55B/U Coax, 53 Ohm

Part No. PE3093				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	85
6"	12"	18"	24"	36"	48"	Custom Len.	
$51.99	$53.99	$54.99	$56.99	$58.99	$61.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3333				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	86
6"	12"	18"	24"	36"	48"	Custom Len.	
$85.99	$85.99	$86.99	$92.99	$88.99	$89.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE3102				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	29.15 dB/100ft		87
6"	12"	18"	24"	36"	48"	Custom Len.	
$69.99	$76.99	$71.99	$72.99	$75.99	$86.99	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE3405				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	88
6"	12"	18"	24"	36"	48"	Custom Len.	
$81.99	$82.99	$83.99	$84.99	$86.99	$87.99	See Web	

SMA MALE TO
SMA FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38240				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		89
12"	24"	36"	48"	60"	-	Custom Len.	
$67.99	$64.99	$65.99	$67.99	$68.99	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

PE-C195 Coax, 50 Ohm

Part No. PE36417				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	90
12"	24"	36"	48"	60"	-	Custom Len.	
$51.99	$53.99	$54.99	$56.99	$58.99	-	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5242				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			91
12"	24"	36"	48"	60"	50CM	Custom Len.	
$283.99	$311.99	$337.99	$363.99	$389.99	$301.99	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7866				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		92
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$64.99	$68.99	$73.99	$77.99	$63.99	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34245					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.047" dia.	36 dB/100ft	32 W	93
6"	12"	18"	24"	36"	48"	Custom Len.		
$119.99	$125.99	$129.99	$133.99	$141.99	$151.99	See Web		

PE-SR401FL Coax, 50 Ohm

Part No. PE34249					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						7.6 dB/100ft	1,400 W	94
6"	12"	18"	24"	36"	48"	Custom Len.		
$135.99	$143.99	$153.99	$161.99	$179.99	$197.99	See Web		

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39441					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.161" dia.	11.89 dB/100ft	450 W	95
6"	9"	12"	18"	24"	-	Custom Len.		
$50.99	$46.39	$50.99	$56.99	$61.99	-	See Web		

PE-SR405FL Coax, 50 Ohm

Part No. PE39419					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22.5 dB/100ft	105 W	96
4"	6"	9"	12"	18"	24"	Custom Len.		
$53.99	$60.99	$57.99	$60.99	$67.99	$74.99	See Web		
Part No. PE3961					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22.5 dB/100ft	130 W	97
6"	12"	18"	24"	36"	48"	Custom Len.		
$79.99	$86.99	$93.99	$92.99	$107.99	$119.99	See Web		

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39433					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.098" dia.	19.5 dB/100ft	130 W	98
6"	9"	12"	18"	24"	-	Custom Len.		
$23.39	$48.79	$23.39	$28.99	$33.39	-	See Web		

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3956				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			99
6"	12"	18"	24"	36"	48"	Custom Len.	
$59.99	$59.99	$59.99	$60.99	$60.99	$61.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3494				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	1
6"	12"	18"	24"	36"	48"	Custom Len.	
$67.99	$71.99	$75.99	$78.99	$80.99	$94.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3184				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	2
6"	12"	18"	24"	36"	48"	Custom Len.	
$74.99	$75.99	$75.99	$75.99	$76.99	$77.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3959				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	3
6"	12"	18"	24"	36"	48"	Custom Len.	
$65.99	$69.99	$70.99	$71.99	$72.99	$69.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3051				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	4
6"	12"	18"	24"	36"	48"	Custom Len.	
$63.99	$64.99	$62.99	$68.99	$66.99	$74.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3553				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	5
6"	12"	18"	24"	36"	48"	Custom Len.	
$66.99	$62.99	$64.99	$72.99	$69.99	$80.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3835				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	6
6"	12"	18"	24"	36"	48"	Custom Len.	
$66.99	$68.99	$70.99	$67.99	$70.99	$74.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3924				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	7
6"	12"	18"	24"	36"	48"	Custom Len.	
$77.99	$82.99	$80.99	$91.99	$93.99	$101.99	See Web	

PE-P086EAM Coax, 50 Ohm

Part No. PE3CA1042				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.104" dia.			8
12"	24"	36"	100"	50CM	100CM	Custom Len.	
$80.99	$96.99	$125.99	Call	Call	$143.99	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE3799				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	9
6"	12"	18"	24"	36"	48"	Custom Len.	
$68.99	$73.99	$79.99	$90.99	$103.99	$107.99	See Web	

Standard Semi-Rigid Cable Assemblies

PE-020SR Coax, 50 Ohm

Part No. PE34241				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					85 dB/100ft	2.9 W	10
6"	12"	18"	24"	36"	48"	Custom Len.	
$165.99	$175.99	$185.99	$197.99	$217.99	$239.99	See Web	

PE-034SR Coax, 50 Ohm

Part No. PE34243				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					60 dB/100ft	10 W	11
6"	12"	18"	24"	36"	48"	Custom Len.	
$169.99	$177.99	$183.99	$191.99	$205.99	$221.99	See Web	

PE-047SR Coax, 50 Ohm

Part No. PE3531				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	12
6"	12"	18"	24"	36"	48"	Custom Len.	
$121.99	$127.99	$133.99	$139.99	$151.99	$163.99	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE3382				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	13
6"	12"	18"	24"	36"	48"	Custom Len.	
$121.99	$127.99	$131.99	$137.99	$147.99	$159.99	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34247				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	14
6"	12"	18"	24"	36"	48"	Custom Len.	
$155.99	$155.99	$167.99	$177.99	$199.99	$221.99	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34252				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	15
6"	12"	18"	24"	36"	48"	Custom Len.	
$76.99	$75.99	$81.99	$86.99	$98.99	$109.99	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34254				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	16
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.99	$71.99	$83.99	$81.99	$92.99	$103.99	See Web	

RG401/U Coax, 50 Ohm

Part No. PE34256				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	17
6"	12"	18"	24"	36"	48"	Custom Len.	
$141.99	$155.99	$167.99	$181.99	$207.99	$233.99	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3825				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	18
6"	12"	18"	24"	36"	48"	Custom Len.	
$75.99	$74.99	$78.99	$83.99	$92.99	$101.99	See Web	
Part No. PE3C2892				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	19
6"	12"	18"	24"	36"	48"	Custom Len.	
$56.99	$56.99	$69.99	$73.99	$82.99	$91.99	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3826				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	20
6"	12"	18"	24"	36"	48"	Custom Len.	
$73.99	$80.99	$85.99	$90.99	$90.99	$99.99	See Web	

Standard Flexible Cable Assemblies

RG55B/U Coax, 53 Ohm

Part No. PE3940				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	21
6"	12"	18"	24"	36"	48"	Custom Len.	
$63.99	$63.99	$64.99	$65.99	$68.99	$71.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3871				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	22
6"	12"	18"	24"	36"	48"	Custom Len.	
$78.99	$79.99	$80.99	$80.99	$81.99	$82.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

RG179B/U Coax, 75 Ohm

Part No. PE3967				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	23
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.99	$71.99	$72.99	$74.99	$77.99	$86.99	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE3806				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	24
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.99	$81.99	$82.99	$83.99	$84.99	$86.99	See Web	

SMA MALE TO
REVERSE POLARITY SMA MALE



Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE37900				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		25
12"	24"	36"	48"	60"	-	Custom Len.	
$64.99	$65.99	$63.99	$64.99	$65.99	-	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3W00906				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		26
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.99	$73.99	$74.99	$75.99	$76.99	$72.99	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE34116				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	27
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.99	$74.99	$70.99	$70.99	$71.99	$72.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE34614				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	28
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.99	$71.99	$78.99	$85.99	$92.99	$99.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE34331				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	29
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.99	$64.99	$64.99	$65.99	$66.99	$66.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE35208				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	30
12"	24"	36"	48"	60"	72"	Custom Len.	
$88.99	$90.99	$83.99	$84.99	$85.99	$86.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE35210				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	31
12"	24"	36"	48"	60"	72"	Custom Len.	
$65.99	$68.99	$71.99	$73.99	$76.99	$79.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE34398				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	32
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.99	$63.99	$67.99	$70.99	$74.99	$83.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE35212				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	33
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.99	$70.99	$74.99	$73.99	$76.99	$80.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE36963				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	34
12"	24"	36"	48"	60"	-	Custom Len.	
$71.99	$69.99	$78.99	$76.99	$80.99	-	See Web	

SMA MALE TO
REVERSE THREAD SMA MALE



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE35351				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	35
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.99	$64.99	$64.99	$65.99	$66.99	$67.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE35355				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	36
12"	24"	36"	48"	60"	72"	Custom Len.	
$65.99	$72.99	$79.99	$86.99	$93.99	$99.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE35359				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	37
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.99	$66.99	$67.99	$67.99	$68.99	$69.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE35363				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	38
12"	24"	36"	48"	60"	72"	Custom Len.	
$75.99	$76.99	$77.99	$78.99	$79.99	$80.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE35367				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	39
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.99	$70.99	$73.99	$75.99	$78.99	$81.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE35371				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	40
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.99	$70.99	$74.99	$78.99	$81.99	$85.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE35375				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	41
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.99	$72.99	$76.99	$80.99	$83.99	$87.99	See Web	

SMA MALE TO
SMB PLUG



Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE34764				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	42
12"	24"	36"	48"	60"	-	Custom Len.	
$73.99	$87.99	$103.99	$117.99	$129.99	-	See Web	

Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm

Part No. PE34455				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.101" dia.			43
6"	12"	18"	24"	36"	48"	Custom Len.	
$65.99	$68.99	$69.99	$73.99	$82.99	$91.99	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3172				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	44
6"	12"	18"	24"	36"	48"	Custom Len.	
$63.99	$68.99	$64.99	$69.99	$70.99	$66.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3181				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		45
6"	12"	18"	24"	36"	48"	Custom Len.	
$61.99	$61.99	$69.99	$68.99	$80.99	$82.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3908				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	46
6"	12"	18"	24"	36"	48"	Custom Len.	
$59.99	$59.99	$59.99	$56.99	$61.99	$61.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3548				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	47
6"	12"	18"	24"	36"	48"	Custom Len.	
$75.99	$76.99	$71.99	$72.99	$79.99	$74.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3755				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	48
6"	12"	18"	24"	36"	48"	Custom Len.	
$59.99	$59.99	$60.99	$61.99	$64.99	$66.99	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE3722				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	49
6"	12"	18"	24"	36"	48"	Custom Len.	
$52.99	$52.99	$54.99	$56.99	$61.99	$64.99	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE34448				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	50
6"	12"	18"	24"	36"	48"	Custom Len.	
$72.99	$72.99	$72.99	$73.99	$75.99	$77.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3187				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	51
6"	12"	18"	24"	36"	48"	Custom Len.	
$58.99	$61.99	$60.99	$65.99	$65.99	$73.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

RG316/U Coax, 50 Ohm

Part No. PE3810				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	52
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$59.99	$61.99	$62.99	$64.99	$68.99	$72.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE33657				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	53
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$61.99	$64.99	$66.99	$68.99	$72.99	$76.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34452				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	54
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$72.99	$80.99	$77.99	$81.99	$98.99	$98.99	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE35527				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	55
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$66.99	$80.99	$83.99	$91.99	$101.99	-	See Web	

SMA MALE TO SMB PLUG RIGHT ANGLE



Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE3W00416				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	56
1 piece price shown. See web or call for volume pricing.				0.109" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$42.99	$44.59	$46.39	$47.99	$49.59	$44.19	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W04476				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	57
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$52.99	$53.99	$53.99	$54.99	$55.99	$52.99	See Web	

SMA MALE TO SMB JACK



Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W03014				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	58
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$49.59	$53.99	$57.99	$61.99	$65.99	$52.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3W05361				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	59
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$80.99	$84.99	$88.99	$92.99	$96.99	$83.99	See Web	

SMA MALE TO SMC PLUG



Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm

Part No. PE34460				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	60
1 piece price shown. See web or call for volume pricing.				0.101" dia.			
6"	12"	14"	18"	24"	36"	Custom Len.	
$55.99	$59.99	Call	$63.99	$67.99	$76.99	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3210				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	61
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$67.99	$67.99	$68.99	$68.99	$69.99	$70.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3944				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	62
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$64.99	$64.99	$65.99	$65.99	$65.99	$66.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3561				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	63
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$65.99	$66.99	$66.99	$67.99	$68.99	$69.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3736				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	64
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$52.99	$53.99	$55.99	$56.99	$59.99	$61.99	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE34458				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	65
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$57.99	$57.99	$60.99	$61.99	$65.99	$70.99	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE34450				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	66
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$72.99	$72.99	$73.99	$74.99	$76.99	$77.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3226				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	67
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$63.99	$63.99	$65.99	$67.99	$70.99	$74.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3809				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	68
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$60.99	$60.99	$61.99	$68.99	$66.99	$70.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34456				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	69
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$52.99	$52.99	$54.99	$59.99	$62.99	$62.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34454				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	70
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$68.99	$72.99	$76.99	$81.99	$89.99	$98.99	See Web	

SMA MALE TO SMP FEMALE



Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE36164				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	71
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$111.99	$119.99	$121.99	$139.99	$139.99	$147.99	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE36166				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	72
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.99	$87.99	$96.99	$107.99	$109.99	$117.99	See Web	

SMA MALE TO SMP FEMALE RIGHT ANGLE



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W06701				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	73
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$83.99	$94.99	$105.99	$117.99	$125.99	$90.99	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C3028				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	74
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.99	$68.99	$71.99	$75.99	$79.99	$66.99	See Web	

Part No. PE3W05274				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	75
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$75.99	$79.99	$83.99	$87.99	$73.99	See Web	

SMA MALE TO SSMA MALE



Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE3W01283				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	76
1 piece price shown. See web or call for volume pricing.				0.109" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.99	$64.99	$66.99	$67.99	$69.99	$63.99	See Web	

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE35430	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.1" dia.	32 dB/100ft	16 W	77
6"	12"	18"	24"	36"	48"	Custom Len.
$79.99	$72.99	$72.99	$72.99	$73.99	$73.99	See Web

RG178B/U Coax, 50 Ohm

Part No. PE3058	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.072" dia.	44.41 dB/100ft	55 W	78
6"	12"	18"	24"	36"	48"	Custom Len.
$86.99	$81.99	$82.99	$82.99	$89.99	$90.99	See Web

RG316/U Coax, 50 Ohm

Part No. PE3669	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.098" dia.	38 dB/100ft	160 W	79
6"	12"	18"	24"	36"	48"	Custom Len.
$79.99	$81.99	$83.99	$78.99	$82.99	$85.99	See Web

RG316-DS Coax, 50 Ohm

Part No. PE37401	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.114" dia.	30 dB/100ft	160 W	80
12"	24"	36"	48"	60"	-	Custom Len.
$78.99	$82.99	$80.99	$83.99	$87.99	-	See Web

SMA MALE TO SSMC PLUG



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4422	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.11" dia.	24 dB/100ft		81
6"	12"	18"	24"	36"	48"	Custom Len.
$63.99	$63.99	$58.99	$59.99	$65.99	$61.99	See Web

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4444	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.105" dia.	19.5 dB/100ft	121.5 W	82
6"	12"	18"	24"	36"	48"	Custom Len.
$75.99	$80.99	$85.99	$91.99	$91.99	$101.99	See Web

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4391	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.072" dia.	44.41 dB/100ft	55 W	83
6"	12"	18"	24"	36"	48"	Custom Len.
$79.99	$88.99	$89.99	$89.99	$91.99	$92.99	See Web

RG196A/U Coax, 50 Ohm

Part No. PE3W06410	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.08" dia.	49 dB/100ft	78 W	84
12"	24"	36"	48"	60"	50CM	Custom Len.
$82.99	$84.99	$86.99	$87.99	$89.99	$83.99	See Web

RG316/U Coax, 50 Ohm

Part No. PE3C4405	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.098" dia.	38 dB/100ft	160 W	85
6"	12"	18"	24"	36"	48"	Custom Len.
$69.99	$71.99	$77.99	$74.99	$78.99	$81.99	See Web

RG316-DS Coax, 50 Ohm

Part No. PE3C4437	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.114" dia.	9.15 dB/100ft	85 W	86
6"	12"	18"	24"	36"	48"	Custom Len.
$71.99	$73.99	$68.99	$77.99	$73.99	$85.99	See Web

SMA MALE TO SSMC PLUG RIGHT ANGLE



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4423	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.11" dia.	24 dB/100ft		87
6"	12"	18"	24"	36"	48"	Custom Len.
$56.99	$57.99	$57.99	$54.99	$55.99	$60.99	See Web

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4484	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.105" dia.	19.5 dB/100ft	121.5 W	88
6"	12"	18"	24"	36"	48"	Custom Len.
$64.99	$76.99	$74.99	$78.99	$97.99	$97.99	See Web

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4463	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.072" dia.	44.41 dB/100ft	55 W	89
6"	12"	18"	24"	36"	48"	Custom Len.
$69.99	$74.99	$70.99	$71.99	$72.99	$73.99	See Web

RG188-DS Coax, 50 Ohm

Part No. PE3W08402	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.118" dia.	30 dB/100ft	160 W	90
48"	-	-	-	-	-	Custom Len.
$72.99	-	-	-	-	-	See Web

RG316/U Coax, 50 Ohm

Part No. PE3C4406	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.098" dia.	38 dB/100ft	160 W	91
6"	12"	18"	24"	36"	48"	Custom Len.
$62.99	$64.99	$65.99	$67.99	$70.99	$74.99	See Web

RG316-DS Coax, 50 Ohm

Part No. PE3C4471	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.114" dia.	30 dB/100ft	85 W	92
6"	12"	18"	24"	36"	48"	Custom Len.
$58.99	$66.99	$67.99	$63.99	$67.99	$70.99	See Web

SMA MALE TO SSMC JACK



Standard Flexible Cable Assemblies

RG316-DS Coax, 50 Ohm

Part No. PE3W04458	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.114" dia.	30 dB/100ft	85 W	93
12"	24"	36"	48"	60"	50CM	Custom Len.
$64.99	$68.99	$72.99	$76.99	$80.99	$66.99	See Web

SMA MALE TO SSMC JACK BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4445	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.105" dia.	19.5 dB/100ft	121.5 W	94
6"	12"	18"	24"	36"	48"	Custom Len.
$60.99	$64.99	$69.99	$74.99	$83.99	$92.99	See Web

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4392	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.072" dia.	44.41 dB/100ft	55 W	95
6"	12"	18"	24"	36"	48"	Custom Len.
$74.99	$80.99	$76.99	$76.99	$77.99	$78.99	See Web

SMA MALE TO TNC MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE36058	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.195" dia.	11.3 dB/100ft	150 W	96
12"	24"	36"	48"	60"	-	Custom Len.
$50.99	$51.99	$52.99	$49.19	$50.99	-	See Web

PE-C240 Coax, 50 Ohm

Part No. PE38642	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.24" dia.	9.2 dB/100ft	250 W	97
12"	24"	36"	48"	60"	-	Custom Len.
$61.99	$62.99	$63.99	$67.99	$70.99	-	See Web

PE-P142LL Coax, 50 Ohm

Part No. PE3C0847	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.195" dia.	7.2 dB/100ft		98
12"	24"	36"	48"	60"	50CM	Custom Len.
$185.99	$205.99	$225.99	$247.99	$267.99	$197.99	See Web

PE-P160LL Coax, 50 Ohm

Part No. PE3C5258	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.16" dia.			99
12"	24"	36"	48"	60"	50CM	Custom Len.
$263.99	$289.99	$315.99	$341.99	$367.99	$279.99	See Web

LMR-195 Coax, 50 Ohm

Part No. PE3C4164	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.195" dia.	11.8 dB/100ft		1
12"	24"	36"	48"	60"	-	Custom Len.
$68.99	$65.99	$66.99	$67.99	$68.99	-	See Web

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE338	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.3" dia.	5.5 dB/100ft		2
12"	24"	36"	48"	60"	50CM	Custom Len.
$351.99	$385.99	Call	$451.99	$483.99	$373.99	See Web
Part No. PE3C3242	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.	0.3" dia.	5.5 dB/100ft		3
12"	24"	36"	48"	60"	50CM	Custom Len.
$279.99	$311.99	$343.99	$375.99	$407.99	$299.99	See Web

For our complete selection of cable assemblies, please visit our website

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34412				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	4
6"	12"	18"	24"	36"	48"	Custom Len.	
$96.99	$101.99	$105.99	$109.99	$119.99	$125.99	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34422				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	5
6"	12"	18"	24"	36"	48"	Custom Len.	
$187.99	$197.99	$195.99	$205.99	$223.99	$241.99	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE33928				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	6
6"	12"	18"	24"	36"	48"	Custom Len.	
$96.99	$96.99	$101.99	$107.99	$117.99	$125.99	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE34416				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	7
6"	12"	18"	24"	36"	48"	Custom Len.	
$83.99	$83.99	$90.99	$96.99	$109.99	$121.99	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE33669				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	8
12"	24"	36"	48"	60"	-	Custom Len.	
$139.99	$143.99	$155.99	$149.99	$153.99	-	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3154				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	9
12"	24"	36"	48"	60"	72"	Custom Len.	
$52.99	$53.99	$54.99	$55.99	$56.99	$57.99	See Web	

RG141A/U Coax, 50 Ohm

Part No. PE37580				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W	10
12"	24"	36"	48"	60"	-	Custom Len.	
$60.99	$67.99	$74.99	$82.99	$89.99	-	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3664				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	11
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.99	$67.99	$74.99	$82.99	$90.99	$91.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3178				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	12
12"	24"	36"	48"	60"	72"	Custom Len.	
$71.99	$67.99	$72.99	$68.99	$69.99	$74.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE34248				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	13
12"	24"	36"	48"	60"	72"	Custom Len.	
$86.99	$88.99	$84.99	$85.99	$86.99	$87.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE33361				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	14
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.99	$71.99	$74.99	$77.99	$79.99	$82.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE33673				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	15
12"	24"	36"	48"	60"	72"	Custom Len.	
$153.99	$155.99	$157.99	$159.99	$161.99	$163.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3176				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	16
12"	24"	36"	48"	60"	72"	Custom Len.	
$171.99	$179.99	$189.99	$197.99	$205.99	$215.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3535				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	17
12"	24"	33"	36"	48"	60"	Custom Len.	
$57.99	$60.99	Call	$64.99	$68.99	$68.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3174				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		18
12"	24"	36"	48"	60"	72"	Custom Len.	
$75.99	$79.99	$83.99	$87.99	$91.99	$95.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34246				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	19
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.99	$65.99	$69.99	$72.99	$76.99	$87.99	See Web	

RG393/U Coax, 50 Ohm

Part No. PE34253				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W	20
12"	24"	36"	48"	60"	72"	Custom Len.	
$173.99	$191.99	$211.99	$229.99	$249.99	$269.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE33948				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	21
12"	24"	36"	48"	60"	72"	Custom Len.	
$71.99	$80.99	$89.99	$99.99	$109.99	$111.99	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE33396				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	22
12"	24"	36"	48"	60"	-	Custom Len.	
$60.99	$70.99	$87.99	$92.99	$111.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE34408				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	23
6"	12"	18"	24"	36"	48"	Custom Len.	
$98.99	$105.99	$111.99	$117.99	$127.99	$139.99	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE34410				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	24
6"	12"	18"	24"	36"	48"	Custom Len.	
$97.99	$103.99	$109.99	$115.99	$123.99	$133.99	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34420				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	25
6"	12"	18"	24"	36"	48"	Custom Len.	
$195.99	$189.99	$201.99	$211.99	$233.99	$255.99	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34406				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	26
6"	12"	18"	24"	36"	48"	Custom Len.	
$85.99	$91.99	$91.99	$97.99	$109.99	$119.99	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34414				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	27
6"	12"	18"	24"	36"	48"	Custom Len.	
$76.99	$81.99	$86.99	$91.99	$101.99	$111.99	See Web	

RG401/U Coax, 50 Ohm

Part No. PE34418				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	28
6"	12"	18"	24"	36"	48"	Custom Len.	
$185.99	$197.99	$199.99	$213.99	$239.99	$265.99	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3089				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.1 dB/100ft	450 W	29
6"	12"	18"	24"	36"	48"	Custom Len.	
$88.99	$88.99	$93.99	$97.99	$107.99	$117.99	See Web	

RG405/U Coax, 50 Ohm

Part No. PE33420				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	30
6"	12"	18"	24"	36"	48"	Custom Len.	
$87.99	$87.99	$96.99	$95.99	$105.99	$113.99	See Web	

Standard Flexible Cable Assemblies

RG55B/U Coax, 53 Ohm

Part No. PE34250				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	31
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.99	$57.99	$60.99	$62.99	$65.99	$68.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE36848				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	32
12"	24"	36"	48"	60"	-	Custom Len.	
$60.99	$61.99	$65.99	$63.99	$64.99	-	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE34255				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	33
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.99	$71.99	$74.99	$77.99	$80.99	$83.99	See Web	

SMA MALE TO
TNC MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C0780				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		34
12"	24"	36"	48"	60"	50CM	Custom Len.	
$287.99	$307.99	$329.99	$349.99	$369.99	$301.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

PE-P160LL Coax, 50 Ohm

Part No. PE3C5259				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			35
12"	24"	36"	48"	60"	50CM	Custom Len.	
$337.99	$363.99	$389.99	$417.99	$443.99	$353.99	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W07181				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	36
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$70.99	$81.99	$92.99	$103.99	$67.99	See Web	

SMA MALE TO TNC FEMALE



Standard Flexible Cable Assemblies

LMR-195-FR Coax, 50 Ohm

Part No. PE3C5480				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		37
12"	24"	36"	48"	60"	50CM	Custom Len.	
$49.99	$48.39	$49.79	$50.99	$52.99	$47.99	See Web	

SMA MALE TO TNC FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C2449				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		38
12"	24"	36"	48"	60"	50CM	Custom Len.	
$229.99	$249.99	$269.99	$291.99	$311.99	$241.99	See Web	

Precision Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39475				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	39
6"	9"	12"	18"	24"	-	Custom Len.	
$63.99	$60.99	$63.99	$70.99	Call	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39489				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	40
6"	9"	12"	18"	24"	-	Custom Len.	
$59.99	$55.99	$59.99	Call	$69.99	-	See Web	

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39483				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	400 W	41
6"	9"	12"	18"	24"	-	Custom Len.	
$59.99	$56.99	$59.99	$64.99	$69.99	-	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39497				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	42
6"	9"	12"	18"	24"	-	Custom Len.	
$67.99	$63.99	$67.99	Call	$78.99	-	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W05224				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	43
12"	24"	36"	48"	60"	50CM	Custom Len.	
$67.99	$71.99	$75.99	$79.99	$83.99	$70.99	See Web	

SMA MALE TO REVERSE POLARITY TNC MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE37120				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	44
12"	24"	36"	48"	60"	-	Custom Len.	
$55.99	$51.99	$52.99	$53.99	$60.99	-	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE34853				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	45
12"	24"	36"	48"	60"	72"	Custom Len.	
$57.99	$58.99	$59.99	$60.99	$60.99	$61.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE34854				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	46
12"	24"	36"	48"	60"	72"	Custom Len.	
$58.99	$70.99	$77.99	$79.99	$93.99	$93.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE35242				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	47
12"	24"	36"	48"	60"	72"	Custom Len.	
$79.99	$80.99	$81.99	$83.99	$84.99	$85.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE35244				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	48
12"	24"	36"	48"	60"	72"	Custom Len.	
$65.99	$68.99	$70.99	$73.99	$76.99	$78.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE34397				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	49
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.99	$58.99	$61.99	$65.99	$68.99	$72.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34396				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	50
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.99	$75.99	$79.99	$77.99	$81.99	$85.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE35246				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	51
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.99	$70.99	$79.99	$87.99	$96.99	$105.99	See Web	

SMA MALE TO TRIMMED LEAD SEXLESS



Test Probe Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE3C8137				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					36 dB/100ft	32 W	52
3"	6"	9"	12"	-	-	Custom Len.	
$74.99	$74.99	$74.99	$74.99	-	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3C8144				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	53
3"	6"	9"	12"	-	-	Custom Len.	
$45.79	$45.79	$45.79	$45.79	-	-	See Web	

SMA MALE TO STRAIGHT CUT LEAD SEXLESS



Test Probe Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE3C8138				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					36 dB/100ft	32 W	54
3"	6"	9"	12"	-	-	Custom Len.	
$74.99	$74.99	$74.99	$74.99	-	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE39395				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	55
3"	6"	9"	12"	-	-	Custom Len.	
$48.59	$48.59	$48.59	$48.59	-	-	See Web	

SMA MALE TO HMCX32 1.2 PLUG



Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1030				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			56
3"	6"	12"	-	-	-	Custom Len.	
$14.59	$16.79	$16.79	-	-	-	See Web	

SMA MALE TO UMCX PLUG



Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38881				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.			57
3"	6"	9"	12"	18"	24"	Custom Len.	
$81.99	$83.99	$85.99	$87.99	$92.99	$96.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

SMA MALE TO UMCX 2.1 PLUG



Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm — 58

Part No. PE3CA1028				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.032" dia.		
3"	6"	12"	16"	18"	-	Custom Len.
$19.79	$18.99	$16.79	Call	Call	-	See Web

SMA MALE TO UMCX 2.5 PLUG



Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm — 59

Part No. PE3CA1026				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.07" dia.		
3"	4"	6"	9"	12"	60"	Custom Len.
Call	Call	$16.59	$16.79	$16.79	Call	See Web

RG178-DS Coax, 50 Ohm — 60

Part No. PE3CA1027				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.086" dia.		
3"	6"	9"	12"	-	-	Custom Len.
$14.79	$25.99	$14.59	$18.19	-	-	See Web

PE-81mm Coax, 50 Ohm — 61

Part No. PE3CA1023				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.032" dia.		
3"	6"	12"	-	-	-	Custom Len.
$14.79	$14.59	$18.99	-	-	-	See Web

PE-113mm Coax, 50 Ohm — 62

Part No. PE3CA1024				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.044" dia.		
3"	6"	25CM	12"	18"	-	Custom Len.
$18.39	$18.19	Call	$18.39	$19.99	-	See Web

PE-137mm Coax, 50 Ohm — 63

Part No. PE3CA1025				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.053" dia.		
3"	6"	12"	-	-	-	Custom Len.
$21.99	$22.19	$19.19	-	-	-	See Web

SMA MALE TO WMCX 1.6 PLUG



Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm — 64

Part No. PE3CA1029				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.032" dia.		
3"	6"	12"	-	-	-	Custom Len.
$16.79	$16.79	$16.79	-	-	-	See Web

REVERSE POLARITY SMA MALE TO BNC MALE



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm — 65

Part No. PE35207				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	72"	Custom Len.
$62.99	$68.99	$69.99	$65.99	$65.99	$66.99	See Web

RG142B/U Coax, 50 Ohm — 66

Part No. PE35209				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W
12"	24"	36"	48"	60"	72"	Custom Len.
$57.99	$64.99	$71.99	$84.99	$85.99	$92.99	See Web

RG174A/U Coax, 50 Ohm — 67

Part No. PE3C3332				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W
12"	24"	36"	48"	60"	72"	Custom Len.
$54.99	$60.99	$55.99	$56.99	$56.99	$57.99	See Web

RG178B/U Coax, 50 Ohm — 68

Part No. PE35213				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W
12"	24"	36"	48"	60"	72"	Custom Len.
$84.99	$86.99	$87.99	$88.99	$95.99	$90.99	See Web

RG188A/U Coax, 50 Ohm — 69

Part No. PE3C3412				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$56.99	$58.99	$61.99	$63.99	$65.99	$68.99	See Web

RG223/U Coax, 50 Ohm — 70

Part No. PE35217				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W
12"	24"	36"	48"	60"	72"	Custom Len.
$57.99	$57.99	$64.99	$64.99	$68.99	$71.99	See Web

RG316/U Coax, 50 Ohm — 71

Part No. PE3C3413				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$57.99	$66.99	$70.99	$67.99	$71.99	$74.99	See Web

REVERSE POLARITY SMA MALE TO MCX PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm — 72

Part No. PE3C0481				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$72.99	$76.99	$75.99	$79.99	$88.99	$86.99	See Web

REVERSE POLARITY SMA MALE TO N MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm — 73

Part No. PE36072				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W
12"	24"	36"	48"	60"	-	Custom Len.
$62.99	$63.99	$63.99	$64.99	$65.99	-	See Web

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm — 74

Part No. PE34727				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	72"	Custom Len.
$66.99	$67.99	$74.99	$69.99	$70.99	$71.99	See Web

RG142B/U Coax, 50 Ohm — 75

Part No. PE34361				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W
12"	24"	36"	48"	60"	72"	Custom Len.
$70.99	$73.99	$85.99	$93.99	$95.99	$109.99	See Web

RG174A/U Coax, 50 Ohm — 76

Part No. PE35221				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W
12"	24"	36"	48"	60"	72"	Custom Len.
$69.99	$76.99	$70.99	$71.99	$71.99	$72.99	See Web

RG178B/U Coax, 50 Ohm — 77

Part No. PE35223				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W
12"	24"	36"	48"	60"	72"	Custom Len.
$91.99	$97.99	$93.99	$94.99	$95.99	$97.99	See Web

RG188A/U Coax, 50 Ohm — 78

Part No. PE35225				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$75.99	$74.99	$76.99	$79.99	$82.99	$85.99	See Web

RG223/U Coax, 50 Ohm — 79

Part No. PE35227				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W
12"	24"	36"	48"	60"	72"	Custom Len.
$63.99	$66.99	$70.99	$78.99	$82.99	$81.99	See Web

RG316/U Coax, 50 Ohm — 80

Part No. PE34770				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$76.99	$76.99	$79.99	$83.99	$86.99	$90.99	See Web

RG400/U Coax, 50 Ohm — 81

Part No. PE34323				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W
12"	24"	36"	48"	60"	-	Custom Len.
$75.99	$80.99	$94.99	$97.99	$113.99	-	See Web

PE-P195 Coax, 50 Ohm — 82

Part No. PE35508				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W
12"	24"	36"	48"	60"	-	Custom Len.
$77.99	$88.99	$99.99	$111.99	$121.99	-	See Web

REVERSE POLARITY SMA MALE TO N FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

RG58C/U Coax, 50 Ohm

Part No. PE3W02336				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	80 W	83
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.99	$70.99	$71.99	$72.99	$73.99	$70.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE34575				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	84
12"	24"	36"	48"	60"	-	Custom Len.	
$72.99	$79.99	$86.99	$93.99	$101.99	-	See Web	

REVERSE POLARITY SMA MALE TO REVERSE POLARITY SMA MALE



Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE34750					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.195" dia.	13 dB/100ft	650 W	85
12"	18"	24"	36"	48"	60"	Custom Len.		
$68.99	$72.99	$76.99	$83.99	$85.99	$92.99	See Web		

REVERSE POLARITY SMA MALE TO REVERSE POLARITY SMA FEMALE



Standard Flexible Cable Assemblies

RG141A/U Coax, 50 Ohm

Part No. PE3C5980				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W	86
12"	24"	36"	48"	60"	50CM	Custom Len.	
$97.99	$115.99	$123.99	$131.99	$141.99	$111.99	See Web	

REVERSE POLARITY SMA MALE TO TNC MALE



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE35214				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	87
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.99	$69.99	$64.99	$65.99	$66.99	$67.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE35216				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	88
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.99	$72.99	$79.99	$86.99	$93.99	$101.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE35218				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	89
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.99	$70.99	$70.99	$71.99	$71.99	$72.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE35220				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	90
12"	24"	36"	48"	60"	72"	Custom Len.	
$87.99	$98.99	$90.99	$91.99	$92.99	$93.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE35222				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	91
12"	24"	36"	48"	60"	72"	Custom Len.	
$71.99	$73.99	$76.99	$79.99	$81.99	$84.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE35224				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	92
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.99	$65.99	$68.99	$72.99	$75.99	$79.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE35226				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	93
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.99	$81.99	$85.99	$88.99	$98.99	$95.99	See Web	

REVERSE THREAD SMA MALE TO REVERSE THREAD SMA MALE



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE35349				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	94
12"	24"	36"	48"	60"	72"	Custom Len.	
$76.99	$77.99	$77.99	$78.99	$79.99	$80.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE35353				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	95
12"	24"	36"	48"	60"	72"	Custom Len.	
$79.99	$86.99	$93.99	$101.99	$107.99	$113.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE35357				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	96
12"	24"	36"	48"	60"	72"	Custom Len.	
$87.99	$87.99	$88.99	$88.99	$89.99	$89.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE35361				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	97
12"	24"	36"	48"	60"	72"	Custom Len.	
$81.99	$82.99	$83.99	$84.99	$86.99	$96.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE35365				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	98
12"	24"	36"	48"	60"	72"	Custom Len.	
$83.99	$86.99	$88.99	$91.99	$94.99	$96.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE35369				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	99
12"	24"	36"	48"	60"	72"	Custom Len.	
$82.99	$86.99	$89.99	$93.99	$96.99	$101.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE35373				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	1
12"	24"	36"	48"	60"	72"	Custom Len.	
$84.99	$88.99	$92.99	$95.99	$99.99	$103.99	See Web	

SMA MALE RIGHT ANGLE TO BNC MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38093				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	2
12"	24"	36"	48"	60"	-	Custom Len.	
$58.99	$54.99	$55.99	$56.99	$62.99	-	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3850				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	3
6"	12"	18"	24"	36"	48"	Custom Len.	
$64.99	$64.99	$65.99	$72.99	$73.99	$67.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3780				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	4
6"	12"	18"	24"	36"	48"	Custom Len.	
$56.99	$56.99	$60.99	$63.99	$70.99	$77.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3448				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	5
6"	12"	18"	24"	36"	48"	Custom Len.	
$65.99	$65.99	$65.99	$66.99	$66.99	$66.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE33257				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	6
12"	24"	36"	48"	60"	-	Custom Len.	
$103.99	$105.99	$105.99	$107.99	$109.99	-	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3C3437				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	7
6"	12"	18"	24"	36"	48"	Custom Len.	
$64.99	$69.99	$66.99	$67.99	$76.99	$79.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3733				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	8
6"	12"	18"	24"	36"	48"	Custom Len.	
$74.99	$75.99	$70.99	$79.99	$83.99	$87.99	See Web	

RG303/U Coax, 50 Ohm

Part No. PE39138				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.17" dia.	14 dB/100ft	650 W	9
12"	24"	36"	48"	60"	-	Custom Len.	
$54.99	$63.99	$67.99	$75.99	$82.99	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C3350				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	10
6"	12"	18"	24"	36"	48"	Custom Len.	
$68.99	$73.99	$70.99	$77.99	$81.99	$85.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

RG400/U Coax, 50 Ohm

Part No. PE3642				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W
6"	12"	18"	24"	36"	48"	Custom Len.
$74.99	$77.99	$78.99	$82.99	$91.99	$101.99	See Web

11

PE-P195 Coax, 50 Ohm

Part No. PE33889				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W
12"	24"	36"	48"	60"	-	Custom Len.
$64.99	$75.99	$86.99	$97.99	$117.99	-	See Web

12

SMA MALE RIGHT ANGLE TO BNC FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3681				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	-	Custom Len.
$82.99	$86.99	$84.99	$94.99	$92.99	-	See Web

13

RG400/U Coax, 50 Ohm

Part No. PE34957				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W
12"	24"	36"	48"	60"	-	Custom Len.
$94.99	$96.99	$105.99	$113.99	$121.99	-	See Web

14

SMA MALE RIGHT ANGLE TO MCX PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W10654				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$74.99	$78.99	$82.99	$86.99	$90.99	$72.99	See Web

15

Standard Semi-Rigid Cable Assemblies

PE-SR405AL Coax, 50 Ohm

Part No. PE3W02882				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$65.99	$77.99	$88.99	$99.99	$111.99	$73.99	See Web

16

SMA MALE RIGHT ANGLE TO MCX JACK



Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W02744				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$82.99	$85.99	$89.99	$93.99	$97.99	$84.99	See Web

17

RG316-DS Coax, 50 Ohm

Part No. PE3W01114				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$71.99	$75.99	$79.99	$83.99	$86.99	$74.99	See Web

18

SMA MALE RIGHT ANGLE TO MMCX PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36507				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W
12"	24"	36"	48"	60"	-	Custom Len.
$84.99	$84.99	$85.99	$86.99	$78.99	-	See Web

19

SMA MALE RIGHT ANGLE TO N MALE



Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3238				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$319.99	$351.99	$383.99	$415.99	$447.99	$339.99	See Web

20

Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE3W00921				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$65.99	$72.99	$79.99	$87.99	$94.99	$69.99	See Web

21

SMA MALE RIGHT ANGLE TO N MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C1528				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$389.99	$409.99	$429.99	$451.99	$471.99	$401.99	See Web

22

LMR-195 Coax, 50 Ohm

Part No. PE3W00852				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$66.99	$67.99	$68.99	$69.99	$70.99	$67.99	See Web

23

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3249				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$580.00	$610.00	$645.00	$675.00	$705.00	$600.00	See Web

24

Standard Flexible Cable Assemblies

LMR-195-FR Coax, 50 Ohm

Part No. PE3W05298				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$68.99	$69.99	$71.99	$72.99	$73.99	$69.99	See Web

25

SMA MALE RIGHT ANGLE TO N FEMALE



Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3250				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$459.99	$491.99	$525.00	$555.00	$590.00	$479.99	See Web

26

SMA MALE RIGHT ANGLE TO N FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C2985				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$329.99	$349.99	$371.99	$391.99	$413.99	$343.99	See Web

27

Precision Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39456				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W
6"	9"	12"	18"	24"	-	Custom Len.
$66.99	Call	$66.99	$71.99	$76.99	-	See Web

28

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39470				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W
6"	9"	12"	18"	24"	-	Custom Len.
$68.99	Call	$68.99	$74.99	Call	-	See Web

29

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3245				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$535.00	$565.00	$600.00	$630.00	$665.00	$555.00	See Web

30

Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39448				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W
6"	9"	12"	18"	24"	-	Custom Len.
$80.99	$68.99	$80.99	$87.99	Call	-	See Web

31

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39462				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	9"	12"	18"	24"	-	Custom Len.
$75.99	$64.99	$75.99	Call	$86.99	-	See Web

32

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE34351				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W
12"	24"	36"	48"	60"	-	Custom Len.
$105.99	$98.99	$107.99	$99.99	$101.99	-	See Web

33

See Our Website For Current Pricing & Real-Time Stock Availability!

***Coax Performance at 1 GHz** **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

RG316/U Coax, 50 Ohm

Part No. PE33014				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		34
12"	24"	36"	48"	60"	-	Custom Len.	
$94.99	$94.99	$97.99	$107.00	$105.99	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3179				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	35
12"	24"	36"	48"	60"	-	Custom Len.	
$95.99	$99.99	$115.99	$117.99	$123.99	-	See Web	

SMA MALE RIGHT ANGLE TO QMA MALE



Low PIM Flexible Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5893				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	36
12"	24"	36"	48"	60"	50CM	Custom Len.	
$82.99	$89.99	$96.99	$103.99	$111.99	$86.99	See Web	

SMA MALE RIGHT ANGLE TO QN FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3W08408				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	37
12"	50CM	100CM	200CM	-	-	Custom Len.	
$111.99	$113.99	$129.99	$163.99	-	-	See Web	

SMA MALE RIGHT ANGLE TO SMA MALE



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39431				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	38
6"	9"	12"	18"	24"	-	Custom Len.	
$52.99	$49.59	$52.99	$57.99	$62.99	-	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W06425				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		39
12"	24"	36"	48"	60"	50CM	Custom Len.	
$67.99	$71.99	$75.99	$79.99	$84.99	$70.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3W06660				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	40
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.99	$77.99	$81.99	$85.99	$89.99	$75.99	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE342				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	8.2 dB/100ft	820 W	41
12"	24"	36"	48"	60"	50CM	Custom Len.	
$251.99	$271.99	$291.99	$313.99	$333.99	$263.99	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3822					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22 dB/100ft	130 W	42
6"	12"	18"	24"	36"	48"	Custom Len.		
$89.99	$89.99	$93.99	$97.99	$115.99	$115.99	See Web		

SMA MALE RIGHT ANGLE TO SMA MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE35347				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	43
12"	24"	36"	48"	60"	-	Custom Len.	
$70.99	$66.99	$67.99	$68.99	$69.99	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE38920				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	44
12"	24"	36"	48"	60"	-	Custom Len.	
$101.99	$99.99	$103.99	$105.99	$107.00	-	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE3C1425				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		45
12"	24"	36"	48"	60"	50CM	Custom Len.	
$361.99	$381.99	$403.99	$423.99	$443.99	$375.99	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5248				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			46
12"	24"	36"	48"	60"	50CM	Custom Len.	
$357.99	$383.99	$409.99	$437.99	$463.99	$373.99	See Web	

Low PIM Flexible Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5895				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	47
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.99	$82.99	$89.99	$96.99	$103.99	$79.99	See Web	

TFT-402 Coax, 50 Ohm

Part No. PE3C7978				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			48
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$62.99	$67.99	$71.99	$76.99	$56.99	See Web	

TFT-402-LF Coax, 50 Ohm

Part No. PE3C8010				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			49
12"	24"	36"	48"	60"	50CM	Custom Len.	
$53.99	$56.99	$58.99	$61.99	$63.99	$53.99	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7867				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		50
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$63.99	$67.99	$71.99	$76.99	$62.99	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6208				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	51
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.99	$72.99	$79.99	$86.99	$93.99	$69.99	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C2884				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		52
12"	24"	36"	48"	60"	50CM	Custom Len.	
$405.99	$437.99	$469.99	$505.00	$535.00	$425.99	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34209				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	53
6"	12"	18"	24"	36"	48"	Custom Len.	
$185.99	$185.99	$191.99	$195.99	$203.99	$213.99	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34217				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	54
6"	12"	18"	24"	36"	48"	Custom Len.	
$195.99	$193.99	$201.99	$211.99	$229.99	$247.99	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE3417				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	55
6"	12"	18"	24"	36"	48"	Custom Len.	
$98.99	$103.99	$107.99	$113.99	$121.99	$125.99	See Web	
Part No. PE39424				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	56
6"	9"	12"	18"	24"	-	Custom Len.	
$75.99	$72.99	$75.99	$80.99	$85.99	-	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39438				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	57
6"	9"	12"	18"	24"	-	Custom Len.	
$37.79	$35.39	$37.79	$43.19	$48.59	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3646				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	58
6"	12"	18"	24"	36"	48"	Custom Len.	
$121.99	$125.99	$133.99	$133.99	$147.99	$159.99	See Web	
Part No. PE39416				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	59
6"	9"	12"	18"	24"	-	Custom Len.	
$74.99	$74.99	$79.99	$86.99	$93.99	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39430				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	60
6"	9"	12"	18"	24"	-	Custom Len.	
$39.79	$37.39	$39.79	$45.39	$50.99	-	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3655							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.195" dia.	Attn. @ 1 GHz	Power @ 1 GHz	61
6"	12"	18"	24"	36"	48"	Custom Len.	
$72.99	$72.99	$73.99	$69.99	$74.99	$71.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3514							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.195" dia.	Attn. @ 1 GHz 13 dB/100ft	Power @ 1 GHz 650 W	62
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.99	$84.99	$82.99	$86.99	$99.99	$107.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3775							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.1" dia.	Attn. @ 1 GHz 32 dB/100ft	Power @ 1 GHz 16 W	63
6"	12"	18"	24"	36"	48"	Custom Len.	
$81.99	$81.99	$81.99	$82.99	$79.99	$83.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3876							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.072" dia.	Attn. @ 1 GHz 44.4 dB/100ft	Power @ 1 GHz 78 W	64
6"	12"	18"	24"	36"	48"	Custom Len.	
$107.99	$101.99	$109.99	$109.99	$103.99	$105.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3511							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.11" dia.	Attn. @ 1 GHz 26 dB/100ft	Power @ 1 GHz 160 W	65
6"	12"	18"	24"	36"	48"	Custom Len.	
$87.99	$82.99	$90.99	$92.99	$95.99	$90.99	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE3347							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.122" dia.	Attn. @ 1 GHz 30 dB/100ft	Power @ 1 GHz 160 W	66
6"	12"	18"	24"	36"	48"	Custom Len.	
$86.99	$91.99	$88.99	$90.99	$94.99	$99.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3428							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.21" dia.	Attn. @ 1 GHz 13.4 dB/100ft	Power @ 1 GHz 53 W	67
6"	12"	18"	24"	36"	48"	Custom Len.	
$77.99	$78.99	$76.99	$78.99	$81.99	$90.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3515							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.102" dia.	Attn. @ 1 GHz 38 dB/100ft	Power @ 1 GHz	68
6"	12"	18"	24"	36"	48"	Custom Len.	
$82.99	$83.99	$85.99	$87.99	$91.99	$95.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3987							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.114" dia.	Attn. @ 1 GHz 30 dB/100ft	Power @ 1 GHz 160 W	69
6"	12"	18"	24"	36"	48"	Custom Len.	
$84.99	$86.99	$88.99	$90.99	$94.99	$92.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3713							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.195" dia.	Attn. @ 1 GHz 14.7 dB/100ft	Power @ 1 GHz 650 W	70
6"	12"	18"	24"	36"	48"	Custom Len.	
$91.99	$91.99	$103.99	$99.99	$117.99	$117.99	See Web	

PE-P086EAM Coax, 50 Ohm

Part No. PE3CA1041							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.104" dia.	Attn. @ 1 GHz	Power @ 1 GHz	71
7"	12"	13"	24"	36"	50CM	Custom Len.	
$87.99	$103.99	$117.99	$123.99	-	-	See Web	

PE-P141 Coax, 50 Ohm

Part No. PE3C1203							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.163" dia.	Attn. @ 1 GHz 11.2 dB/100ft	Power @ 1 GHz 550 W	72
12"	24"	36"	48"	60"	50CM	Custom Len.	
$233.99	$247.99	$261.99	$277.99	$291.99	$241.99	See Web	

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1037							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.163" dia.	Attn. @ 1 GHz	Power @ 1 GHz	73
12"	20.500	24"	36"	50CM	100CM	Custom Len.	
$101.99	Call	$123.99	$147.99	Call	$153.99	See Web	

Standard Semi-Rigid Cable Assemblies

PE-020SR Coax, 50 Ohm

Part No. PE34211							
1 piece price shown. See web or call for volume pricing.				Cable Dia.	Attn. @ 1 GHz 85 dB/100ft	Power @ 1 GHz 2.9 W	74
6"	12"	18"	24"	36"	48"	Custom Len.	
$187.99	$197.99	$207.99	$219.99	$239.99	$261.99	See Web	

PE-034SR Coax, 50 Ohm

Part No. PE34219							
1 piece price shown. See web or call for volume pricing.				Cable Dia.	Attn. @ 1 GHz 60 dB/100ft	Power @ 1 GHz 10 W	75
6"	12"	18"	24"	36"	48"	Custom Len.	
$161.99	$169.99	$177.99	$183.99	$199.99	$213.99	See Web	

PE-047SR Coax, 50 Ohm

Part No. PE3147							
1 piece price shown. See web or call for volume pricing.				Cable Dia.	Attn. @ 1 GHz 40 dB/100ft	Power @ 1 GHz 32 W	76
6"	12"	18"	24"	36"	48"	Custom Len.	
$173.99	$179.99	$185.99	$191.99	$203.99	$215.99	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE3259							
1 piece price shown. See web or call for volume pricing.				Cable Dia.	Attn. @ 1 GHz 41 dB/100ft	Power @ 1 GHz 32 W	77
6"	12"	18"	24"	36"	48"	Custom Len.	
$173.99	$177.99	$183.99	$189.99	$199.99	$209.99	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34215							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.25" dia.	Attn. @ 1 GHz 8 dB/100ft	Power @ 1 GHz 1,400 W	78
6"	12"	18"	24"	36"	48"	Custom Len.	
$195.99	$195.99	$207.99	$217.99	$239.99	$261.99	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34208							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.141" dia.	Attn. @ 1 GHz 13 dB/100ft	Power @ 1 GHz 450 W	79
6"	12"	18"	24"	36"	48"	Custom Len.	
$105.99	$111.99	$117.99	$121.99	$125.99	$137.99	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34213							
1 piece price shown. See web or call for volume pricing.				Cable Dia.	Attn. @ 1 GHz 23 dB/100ft	Power @ 1 GHz 130 W	80
6"	12"	18"	24"	36"	48"	Custom Len.	
$111.99	$115.99	$119.99	$123.99	$133.99	$143.99	See Web	

RG401/U Coax, 50 Ohm

Part No. PE34223							
1 piece price shown. See web or call for volume pricing.				Cable Dia.	Attn. @ 1 GHz 7.5 dB/100ft	Power @ 1 GHz 870 W	81
6"	12"	18"	24"	36"	48"	Custom Len.	
$205.99	$205.99	$217.99	$231.99	$259.99	$285.99	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3819							
1 piece price shown. See web or call for volume pricing.				Cable Dia.	Attn. @ 1 GHz 12 dB/100ft	Power @ 1 GHz 650 W	82
6"	12"	18"	24"	36"	48"	Custom Len.	
$105.99	$109.99	$109.99	$113.99	$127.99	$129.99	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3820							
1 piece price shown. See web or call for volume pricing.				Cable Dia.	Attn. @ 1 GHz 22 dB/100ft	Power @ 1 GHz 130 W	83
6"	12"	18"	24"	36"	48"	Custom Len.	
$111.99	$115.99	$119.99	$121.99	$131.99	$139.99	See Web	

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE3380							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.242" dia.	Attn. @ 1 GHz 11.5 dB/100ft	Power @ 1 GHz 77 W	84
6"	12"	18"	24"	36"	48"	Custom Len.	
$99.99	$99.99	$101.99	$101.99	$103.99	$103.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE3858							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.1" dia.	Attn. @ 1 GHz 25 dB/100ft	Power @ 1 GHz 200 W	85
6"	12"	18"	24"	36"	48"	Custom Len.	
$90.99	$90.99	$92.99	$93.99	$96.99	$99.99	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE3444							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.242" dia.	Attn. @ 1 GHz 13 dB/100ft	Power @ 1 GHz 77 W	86
6"	12"	18"	24"	36"	48"	Custom Len.	
$101.99	$103.99	$103.99	$103.99	$105.99	$107.99	See Web	

RG180B/U Coax, 95 Ohm

Part No. PE3141							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.141" dia.	Attn. @ 1 GHz	Power @ 1 GHz 250 W	87
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.99	$80.99	$83.99	$85.99	$90.99	$95.99	See Web	

SMA MALE RIGHT ANGLE TO SMA FEMALE



Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C2305							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.195" dia.	Attn. @ 1 GHz 10 dB/100ft	Power @ 1 GHz	88
12"	24"	36"	48"	60"	50CM	Custom Len.	
$289.99	$309.99	$329.99	$351.99	$371.99	$301.99	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7868							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.303" dia.	Attn. @ 1 GHz 5.85 dB/100ft	Power @ 1 GHz	89
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.99	$63.99	$66.99	$71.99	$75.99	$61.99	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W02994							
1 piece price shown. See web or call for volume pricing.				Cable Dia. 0.098" dia.	Attn. @ 1 GHz 19.5 dB/100ft	Power @ 1 GHz 121.5 W	90
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.99	$70.99	$81.99	$92.99	$103.99	$66.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

SMA MALE RIGHT ANGLE TO SMA FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38574				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		91
12"	24"	36"	48"	60"	-	Custom Len.	
$66.99	$68.99	$69.99	$71.99	$72.99	-	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5244				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			92
12"	24"	36"	48"	60"	50CM	Custom Len.	
$331.99	$357.99	$383.99	$411.99	$437.99	$349.99	See Web	

Precision Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39428				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	93
6"	9"	12"	18"	24"	-	Custom Len.	
$53.99	$50.99	$53.99	$58.99	$62.99	-	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39442				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	94
6"	9"	12"	18"	24"	33"	Custom Len.	
$55.99	$52.99	Call	Call	$65.99	Call	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7869				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		95
12"	24"	36"	48"	60"	50CM	Custom Len.	
$61.99	$65.99	$70.99	$74.99	$78.99	$64.99	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34307				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	96
6"	12"	18"	24"	36"	48"	Custom Len.	
$159.99	$163.99	$167.99	$171.99	$179.99	$189.99	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34319				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	97
6"	12"	18"	24"	36"	48"	Custom Len.	
$151.99	$161.99	$169.99	$179.99	$197.99	$215.99	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE34299				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	98
6"	12"	18"	24"	36"	48"	Custom Len.	
$90.99	$87.99	$92.99	$96.99	$107.99	$115.99	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE39420				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	99
6"	9"	12"	18"	24"	-	Custom Len.	
$62.99	$59.99	$62.99	$69.99	$75.99	-	See Web	

Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE3759				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	1
6"	12"	18"	24"	36"	48"	Custom Len.	
$74.99	$72.99	$76.99	$79.99	$86.99	$93.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3149				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	2
6"	12"	18"	24"	36"	48"	Custom Len.	
$82.99	$82.99	$89.99	$83.99	$90.99	$91.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3152				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	3
6"	12"	18"	24"	36"	48"	Custom Len.	
$82.99	$85.99	$86.99	$83.99	$88.99	$85.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3050				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	4
6"	12"	18"	24"	36"	48"	Custom Len.	
$84.99	$90.99	$85.99	$86.99	$96.99	$92.99	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE34179				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	5
6"	12"	18"	24"	36"	48"	Custom Len.	
$87.99	$84.99	$86.99	$89.99	$93.99	$97.99	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE34141				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	6
6"	12"	18"	24"	36"	48"	Custom Len.	
$85.99	$85.99	$86.99	$86.99	$88.99	$90.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3800				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	7
6"	12"	18"	24"	36"	48"	Custom Len.	
$72.99	$69.99	$70.99	$72.99	$76.99	$79.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3836				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	8
6"	12"	18"	24"	36"	48"	Custom Len.	
$83.99	$83.99	$85.99	$87.99	$90.99	$94.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34061				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	9
6"	12"	18"	24"	36"	48"	Custom Len.	
$85.99	$83.99	$85.99	$87.99	$90.99	$94.99	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE33749				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	10
6"	12"	18"	24"	36"	48"	Custom Len.	
$85.99	$85.99	$91.99	$96.99	$107.99	$119.99	See Web	

Standard Semi-Rigid Cable Assemblies

PE-020SR Coax, 50 Ohm

Part No. PE34309				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					85 dB/100ft	2.9 W	11
6"	12"	18"	24"	36"	48"	Custom Len.	
$187.99	$197.99	$207.99	$217.99	$239.99	$261.99	See Web	

PE-034SR Coax, 50 Ohm

Part No. PE34321				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					60 dB/100ft	10 W	12
6"	12"	18"	24"	36"	48"	Custom Len.	
$171.99	$179.99	$185.99	$193.99	$207.99	$223.99	See Web	

PE-047SR Coax, 50 Ohm

Part No. PE34303				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	13
6"	12"	18"	24"	36"	48"	Custom Len.	
$159.99	$165.99	$171.99	$177.99	$189.99	$201.99	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE34305				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	14
6"	12"	18"	24"	36"	48"	Custom Len.	
$159.99	$165.99	$169.99	$175.99	$185.99	$197.99	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34317				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	15
6"	12"	18"	24"	36"	48"	Custom Len.	
$173.99	$173.99	$185.99	$195.99	$217.99	$239.99	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34297				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	16
6"	12"	18"	24"	36"	48"	Custom Len.	
$77.99	$83.99	$89.99	$94.99	$105.99	$117.99	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34311				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	17
6"	12"	18"	24"	36"	48"	Custom Len.	
$103.99	$103.99	$107.99	$113.99	$121.99	$131.99	See Web	

RG401/U Coax, 50 Ohm

Part No. PE34315				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	18
6"	12"	18"	24"	36"	48"	Custom Len.	
$159.99	$171.99	$185.99	$197.99	$223.99	$249.99	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3679				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	19
6"	12"	18"	24"	36"	48"	Custom Len.	
$87.99	$87.99	$92.99	$96.99	$105.99	$115.99	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3925				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	20
6"	12"	18"	24"	36"	48"	Custom Len.	
$101.99	$101.99	$113.99	$111.99	$119.99	$125.99	See Web	

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE34160				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	21
6"	12"	18"	24"	36"	48"	Custom Len.	
$85.99	$86.99	$87.99	$87.99	$88.99	$89.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

RG179B/U Coax, 75 Ohm

Part No. PE34135				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	29.15 dB/100ft	240 W	22
6"	12"	18"	24"	36"	48"	Custom Len.	
$75.99	$77.99	$78.99	$80.99	$83.99	$86.99	See Web	

SMA MALE RIGHT ANGLE TO REVERSE POLARITY SMA MALE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W05106				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	23
12"	24"	36"	48"	60"	50CM	Custom Len.	
$109.99	$123.99	$123.99	$123.99	$125.99	$123.99	See Web	

SMA MALE RIGHT ANGLE TO REVERSE POLARITY SMA FEMALE



Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE3W03763				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft	600 W	24
12"	24"	36"	48"	60"	50CM	Custom Len.	
$82.99	$89.99	$96.99	$105.99	$111.99	$87.99	See Web	

SMA MALE RIGHT ANGLE TO SMB PLUG



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE33482				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	25
12"	24"	36"	48"	60"	-	Custom Len.	
$83.99	$84.99	$85.99	$85.99	$86.99	-	See Web	

SMA MALE RIGHT ANGLE TO SMB PLUG RIGHT ANGLE



Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE3W01739				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	26
12"	24"	36"	48"	60"	50CM	Custom Len.	
$82.99	$95.99	$109.99	$121.99	$135.99	$90.99	See Web	

SMA MALE RIGHT ANGLE TO SMC PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3740				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	27
12"	24"	36"	48"	60"	50CM	Custom Len.	
$77.99	$75.99	$78.99	$82.99	$90.99	$73.99	See Web	

SMA MALE RIGHT ANGLE TO SSMC PLUG



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4424				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		28
6"	12"	18"	24"	36"	48"	Custom Len.	
$75.99	$76.99	$76.99	$77.99	$78.99	$79.99	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4446				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	29
6"	12"	18"	24"	36"	48"	Custom Len.	
$70.99	$75.99	$80.99	$84.99	$93.99	$103.99	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4407				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	30
6"	12"	18"	24"	36"	48"	Custom Len.	
$78.99	$80.99	$81.99	$83.99	$86.99	$90.99	See Web	

SMA MALE RIGHT ANGLE TO SSMC PLUG RIGHT ANGLE



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4425				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		31
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.99	$76.99	$72.99	$73.99	$73.99	$74.99	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4485				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	32
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.99	$76.99	$76.99	$80.99	$90.99	$99.99	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4408				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	33
6"	12"	18"	24"	36"	48"	Custom Len.	
$77.99	$87.99	$81.99	$82.99	$86.99	$89.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4472				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	34
6"	12"	18"	24"	36"	48"	Custom Len.	
$74.99	$81.99	$78.99	$79.99	$83.99	$86.99	See Web	

SMA MALE RIGHT ANGLE TO SSMC JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4447				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	35
6"	12"	18"	24"	36"	48"	Custom Len.	
$68.99	$73.99	$71.99	$76.99	$85.99	$94.99	See Web	

SMA MALE RIGHT ANGLE TO TNC MALE



Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C1179				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		36
6"	12"	24"	36"	48"	60"	Custom Len.	
Call	$285.99	$307.99	$327.99	$347.99	$369.99	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5261				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			37
12"	24"	36"	48"	60"	50CM	Custom Len.	
$309.99	$335.99	$363.99	$389.99	$415.99	$327.99	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C1617				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		38
12"	24"	36"	48"	60"	50CM	Custom Len.	
$357.99	$389.99	$421.99	$453.99	$485.99	$377.99	See Web	

SMA MALE RIGHT ANGLE TO TNC MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C1409				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		39
12"	24"	36"	48"	60"	50CM	Custom Len.	
$411.99	$409.99	$429.99	$451.99	$473.99	$401.99	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5262				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			40
12"	24"	36"	48"	60"	50CM	Custom Len.	
$385.99	$411.99	$437.99	$463.99	$491.99	$401.99	See Web	

SMA MALE RIGHT ANGLE TO TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Low Loss Flexible Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

LMR-195 Coax, 50 Ohm

Part No. PE3C0056				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		41
12"	24"	36"	48"	60"	-	Custom Len.	
$67.99	$68.99	$64.99	$64.99	$65.99	-	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE3C1173				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		42
12"	24"	36"	48"	60"	50CM	Custom Len.	
$351.99	$351.99	$371.99	$393.99	$413.99	$343.99	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5263				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			43
12"	24"	36"	48"	60"	50CM	Custom Len.	
$343.99	$369.99	$395.99	$423.99	$449.99	$359.99	See Web	

Precision Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39484				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	44
6"	9"	12"	18"	24"	-	Custom Len.	
$57.99	$53.99	$57.99	$62.99	$67.99	-	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39498				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	45
6"	9"	12"	18"	24"	-	Custom Len.	
$62.99	$58.99	Call	Call	Call	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE39476				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	46
2.500//	6"	9"	12"	18"	24"	Custom Len.	
Call	$63.99	$65.99	$63.99	$70.99	Call	See Web	

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE3W00169				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						450 W	47
12"	24"	36"	48"	60"	50CM	Custom Len.	
$99.99	$109.99	$119.99	$127.99	$139.99	$107.99	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39490				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	48
6"	9"	12"	18"	24"	-	Custom Len.	
$65.99	$54.99	$65.99	$70.99	$76.99	-	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE33073				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		49
12"	24"	36"	48"	60"	-	Custom Len.	
$99.99	$103.99	$101.99	$111.99	$109.99	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE33759				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	50
12"	24"	36"	48"	60"	-	Custom Len.	
$97.99	$98.99	$107.99	$117.99	$123.99	-	See Web	

SMA MALE RIGHT ANGLE TO
REVERSE POLARITY TNC MALE



Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE3C7914				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		51
12"	24"	36"	48"	60"	50CM	Custom Len.	
$97.99	$105.99	$111.99	$119.99	$125.99	$94.99	See Web	

SMA MALE RIGHT ANGLE TO
NEX10 MALE



Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6259				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	52
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.99	$79.99	$86.99	$93.99	$101.99	$77.99	See Web	

REVERSE POLARITY SMA MALE
RIGHT ANGLE TO



Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE35991				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	53
12"	24"	36"	48"	60"	-	Custom Len.	
$103.99	$119.99	$127.99	$137.99	$135.99	-	See Web	

REVERSE POLARITY SMA MALE
RIGHT ANGLE TO



Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3W02390				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		54
12"	24"	36"	48"	60"	50CM	Custom Len.	
$93.99	$94.99	$94.99	$95.99	$96.99	$93.99	See Web	

REVERSE POLARITY SMA MALE
RIGHT ANGLE TO



Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE3W06085				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	55
12"	24"	36"	48"	60"	50CM	Custom Len.	
$103.99	$113.99	$119.99	$129.99	$139.99	$99.99	See Web	

SMA FEMALE TO
FAKRA PLUG



Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE39344A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		56
12"	24"	36"	48"	60"	-	Custom Len.	
$53.99	$50.99	$51.99	$53.99	$54.99	-	See Web	

Part No. PE39344C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		57
12"	24"	36"	48"	60"	-	Custom Len.	
$53.99	$50.99	$51.99	$53.99	$54.99	-	See Web	

Part No. PE39344D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		58
12"	24"	36"	48"	60"	-	Custom Len.	
$53.99	$55.99	$51.99	$53.99	$54.99	-	See Web	

Part No. PE39344H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		59
12"	24"	36"	48"	60"	-	Custom Len.	
$54.99	$51.99	$53.99	$54.99	$56.99	-	See Web	

Part No. PE39344I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		60
12"	24"	36"	48"	60"	-	Custom Len.	
$53.99	$50.99	$51.99	$53.99	$54.99	-	See Web	

Part No. PE39344K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		61
12"	24"	36"	48"	60"	-	Custom Len.	
$48.59	$55.99	$51.99	$53.99	$54.99	-	See Web	

Part No. PE39344Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		62
12"	24"	36"	48"	60"	-	Custom Len.	
$48.59	$54.99	$51.99	$53.99	$54.99	-	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE39345A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	63
12"	24"	36"	48"	60"	-	Custom Len.	
$56.99	$57.99	$57.99	$58.99	$59.99	-	See Web	

Part No. PE39345C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	64
12"	24"	36"	48"	60"	-	Custom Len.	
$62.99	$57.99	$57.99	$58.99	$59.99	-	See Web	

Part No. PE39345D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	65
12"	24"	36"	48"	60"	-	Custom Len.	
$56.99	$57.99	$57.99	$58.99	$59.99	-	See Web	

Part No. PE39345H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	66
12"	24"	36"	48"	60"	-	Custom Len.	
$56.99	$57.99	$57.99	$58.99	$59.99	-	See Web	

Part No. PE39345I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	67
12"	24"	36"	48"	60"	-	Custom Len.	
$56.99	$57.99	$57.99	$58.99	$59.99	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

Part No. PE39345K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	68
12"	24"	36"	48"	60"	-	Custom Len.	
$56.99	$57.99	$57.99	$58.99	$59.99	-	See Web	
Part No. PE39345Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	69
12"	24"	36"	48"	60"	-	Custom Len.	
$62.99	$57.99	$57.99	$58.99	$59.99	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE39346A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	70
12"	24"	36"	48"	60"	-	Custom Len.	
$64.99	$67.99	$71.99	$75.99	$78.99	-	See Web	
Part No. PE39346C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	71
12"	24"	36"	48"	60"	-	Custom Len.	
$58.99	$61.99	$65.99	$69.99	$72.99	-	See Web	
Part No. PE39346D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	72
12"	24"	36"	48"	60"	-	Custom Len.	
$58.99	$61.99	$65.99	$69.99	$72.99	-	See Web	
Part No. PE39346H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	73
12"	24"	36"	48"	60"	-	Custom Len.	
$58.99	$61.99	$65.99	$69.99	$72.99	-	See Web	
Part No. PE39346I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	74
12"	24"	36"	48"	60"	-	Custom Len.	
$64.99	$67.99	$71.99	$75.99	$78.99	-	See Web	
Part No. PE39346K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	75
12"	24"	36"	48"	60"	-	Custom Len.	
$64.99	$61.99	$65.99	$69.99	$72.99	-	See Web	
Part No. PE39346Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	76
12"	24"	36"	48"	60"	-	Custom Len.	
$58.99	$61.99	$65.99	$69.99	$72.99	-	See Web	

SMA FEMALE TO FAKRA JACK



Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE39349A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		77
12"	24"	36"	48"	60"	-	Custom Len.	
$53.99	$50.99	$51.99	$53.99	$54.99	-	See Web	
Part No. PE39349B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		78
12"	24"	36"	48"	60"	-	Custom Len.	
$53.99	$50.99	$51.99	$53.99	$54.99	-	See Web	
Part No. PE39349C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		79
12"	24"	36"	48"	60"	-	Custom Len.	
$53.99	$50.99	$51.99	$53.99	$60.99	-	See Web	
Part No. PE39349D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		80
12"	24"	36"	48"	60"	-	Custom Len.	
$50.99	$52.99	$50.99	$52.99	$57.99	-	See Web	
Part No. PE39349H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		81
12"	24"	36"	48"	60"	-	Custom Len.	
$53.99	$50.99	$51.99	$53.99	$54.99	-	See Web	
Part No. PE39349I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		82
12"	24"	36"	48"	60"	-	Custom Len.	
$53.99	$50.99	$51.99	$53.99	$54.99	-	See Web	
Part No. PE39349K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		83
12"	24"	36"	48"	60"	-	Custom Len.	
$48.59	$55.99	$51.99	$53.99	$54.99	-	See Web	
Part No. PE39349Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		84
12"	24"	36"	48"	60"	-	Custom Len.	
$53.99	$50.99	$56.99	$53.99	$60.99	-	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE39350A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	85
12"	24"	36"	48"	60"	-	Custom Len.	
$62.99	$62.99	$62.99	$63.99	$63.99	-	See Web	
Part No. PE39350B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	86
12"	24"	36"	48"	60"	-	Custom Len.	
$60.99	$61.99	$62.99	$62.99	$62.99	-	See Web	
Part No. PE39350C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	87
12"	24"	36"	48"	60"	-	Custom Len.	
$62.99	$62.99	$62.99	$63.99	$63.99	-	See Web	
Part No. PE39350D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	88
12"	24"	36"	48"	60"	-	Custom Len.	
$59.99	$57.99	$57.99	$58.99	$59.99	-	See Web	
Part No. PE39350H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	89
12"	24"	36"	48"	60"	-	Custom Len.	
$56.99	$57.99	$57.99	$58.99	$59.99	-	See Web	
Part No. PE39350I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	90
12"	24"	36"	48"	60"	-	Custom Len.	
$56.99	$57.99	$57.99	$58.99	$59.99	-	See Web	
Part No. PE39350K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	91
12"	24"	36"	48"	60"	-	Custom Len.	
$62.99	$62.99	$62.99	$63.99	$63.99	-	See Web	
Part No. PE39350Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	92
12"	24"	36"	48"	60"	-	Custom Len.	
$67.99	$62.99	$62.99	$63.99	$63.99	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE39351A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	93
12"	24"	36"	48"	60"	-	Custom Len.	
$64.99	$67.99	$71.99	$75.99	$78.99	-	See Web	
Part No. PE39351B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	94
12"	24"	36"	48"	60"	-	Custom Len.	
$58.99	$61.99	$65.99	$69.99	$72.99	-	See Web	
Part No. PE39351C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	95
12"	24"	36"	48"	60"	-	Custom Len.	
$70.99	$67.99	$71.99	$75.99	$78.99	-	See Web	
Part No. PE39351D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	96
12"	24"	36"	48"	60"	-	Custom Len.	
$64.99	$67.99	$71.99	$75.99	$78.99	-	See Web	
Part No. PE39351H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	97
12"	24"	36"	48"	60"	-	Custom Len.	
$58.99	$61.99	$65.99	$69.99	$72.99	-	See Web	
Part No. PE39351I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	98
12"	24"	36"	48"	60"	-	Custom Len.	
$58.99	$61.99	$65.99	$69.99	$72.99	-	See Web	
Part No. PE39351K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	99
12"	24"	36"	48"	60"	-	Custom Len.	
$58.99	$61.99	$65.99	$69.99	$72.99	-	See Web	

SMA FEMALE TO MCX PLUG RIGHT ANGLE



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W03859				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	1
12"	24"	36"	48"	60"	50CM	Custom Len.	
$82.99	$93.99	$105.99	$115.99	$125.99	$89.99	See Web	

SMA FEMALE TO MMCX PLUG



Standard Flexible Cable Assemblies

RG188-DS Coax, 50 Ohm

Part No. PE3W03032				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.118" dia.	30 dB/100ft	160 W	2
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.99	$78.99	$83.99	$87.99	$92.99	$76.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

SMA FEMALE TO N MALE



Precision Flexible Cable Assemblies

PE-P141 Coax, 50 Ohm

Part No. PE356				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			3
12"	24"	36"	48"	60"	72"	Custom Len.	
$215.99	$215.99	$243.99	$257.99	$255.99	$285.99	See Web	

SMA FEMALE TO N FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C3159				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		4
12"	24"	36"	48"	60"	50CM	Custom Len.	
$251.99	$271.99	$291.99	$311.99	$331.99	$263.99	See Web	

SMA FEMALE TO NMO MOUNT SEXLESS



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37841				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	5
60"	120"	180"	-	-	-	Custom Len.	
$74.99	$73.99	$77.99	-	-	-	See Web	

SMA FEMALE TO QMA MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38278				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	6
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.99	$63.99	$64.99	$65.99	$66.99	$67.99	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE38277				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	7
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.99	$74.99	$69.99	$70.99	$71.99	$72.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE38276				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	8
12"	24"	36"	48"	60"	72"	Custom Len.	
$85.99	$89.99	$86.99	$90.99	$93.99	$97.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE38052				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	26.1 dB/100ft	160 W	9
12"	24"	36"	48"	60"	72"	Custom Len.	
$95.99	$99.99	$103.99	$107.99	$109.99	$113.99	See Web	

SMA FEMALE TO SMA MALE RIGHT ANGLE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W03981				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	10
12"	24"	36"	48"	60"	50CM	Custom Len.	
$61.99	$61.99	$62.99	$63.99	$64.99	$62.99	See Web	

SMA FEMALE TO SMA FEMALE



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C0045				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		11
12"	24"	36"	48"	60"	-	Custom Len.	
$73.99	$68.99	$69.99	$70.99	$77.99	-	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE3C1239				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		12
12"	24"	36"	48"	60"	50CM	Custom Len.	
$233.99	$255.99	$275.99	$295.99	$317.99	$247.99	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34833				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	13
6"	12"	18"	24"	36"	48"	Custom Len.	
$133.99	$129.99	$133.99	$149.99	$147.99	$155.99	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE3534				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	14
6"	12"	18"	24"	36"	48"	Custom Len.	
$109.99	$119.99	$125.99	$135.99	$153.99	$171.99	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE33964				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	15
6"	12"	18"	24"	36"	48"	Custom Len.	
$75.99	$75.99	$80.99	$85.99	$94.99	$103.99	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE34292				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	16
6"	12"	18"	24"	36"	48"	Custom Len.	
$107.99	$107.99	$115.99	$119.99	$133.99	$147.99	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE33547				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	17
12"	24"	36"	48"	60"	-	Custom Len.	
$77.99	$73.99	$74.99	$81.99	$75.99	-	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3578				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	18
12"	24"	36"	48"	60"	-	Custom Len.	
$59.99	$65.99	$72.99	$86.99	$86.99	-	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE33120				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	19
12"	24"	36"	48"	60"	-	Custom Len.	
$72.99	$79.99	$73.99	$80.99	$75.99	-	See Web	

RG223/U Coax, 50 Ohm

Part No. PE33254				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	20
12"	24"	36"	48"	60"	-	Custom Len.	
$52.99	$56.99	$59.99	$67.99	$65.99	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE33047				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		21
12"	24"	36"	48"	60"	-	Custom Len.	
$79.99	$83.99	$82.99	$91.99	$95.99	-	See Web	

Standard Semi-Rigid Cable Assemblies

PE-020SR Coax, 50 Ohm

Part No. PE34917				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					85 dB/100ft	2.9 W	22
6"	12"	18"	24"	36"	48"	Custom Len.	
$207.99	$219.99	$217.99	$229.99	$251.99	$273.99	See Web	

PE-034SR Coax, 50 Ohm

Part No. PE34405				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					60 dB/100ft	10 W	23
6"	12"	18"	24"	36"	48"	Custom Len.	
$183.99	$189.99	$187.99	$193.99	$209.99	$223.99	See Web	

PE-047SR Coax, 50 Ohm

Part No. PE3758				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	24
6"	12"	18"	24"	36"	48"	Custom Len.	
$129.99	$135.99	$135.99	$149.99	$161.99	$167.99	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE34835				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	25
6"	12"	18"	24"	36"	48"	Custom Len.	
$135.99	$129.99	$133.99	$139.99	$151.99	$161.99	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE3524				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	26
6"	12"	18"	24"	36"	48"	Custom Len.	
$111.99	$119.99	$131.99	$141.99	$163.99	$183.99	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34836				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	27
6"	12"	18"	24"	36"	48"	Custom Len.	
$78.99	$82.99	$84.99	$89.99	$101.99	$113.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

PE-SR405AL Coax, 50 Ohm

Part No. PE34834				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W
6"	12"	18"	24"	36"	48"	Custom Len.
$89.99	$101.99	$99.99	$105.99	$115.99	$123.99	See Web

28

RG401/U Coax, 50 Ohm

Part No. PE3521				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W
6"	12"	18"	24"	36"	48"	Custom Len.
$135.99	$135.99	$147.99	$161.99	$189.99	$215.99	See Web

29

RG402/U Coax, 50 Ohm

Part No. PE3931				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W
6"	12"	18"	24"	36"	48"	Custom Len.
$76.99	$81.99	$86.99	$86.99	$95.99	$105.99	See Web

30

RG405/U Coax, 50 Ohm

Part No. PE3109				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W
6"	12"	18"	24"	36"	48"	Custom Len.
$78.99	$78.99	$82.99	$86.99	$95.99	$103.99	See Web

31

Standard Flexible Cable Assemblies

RG62A/U Coax, 93 Ohm

Part No. PE3424				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W
12"	24"	36"	48"	60"	-	Custom Len.
$80.99	$81.99	$83.99	$84.99	$86.99	-	See Web

32

SMA FEMALE TO SMP FEMALE RIGHT ANGLE



Standard Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W10074				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$43.19	$44.19	$45.19	$45.99	$46.99	$42.99	See Web

33

SMA FEMALE TO SSMC PLUG



Standard Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W06055				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$57.99	$58.99	$58.99	$59.99	$60.99	$57.99	See Web

34

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4426				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
6"	12"	18"	24"	36"	48"	Custom Len.
$68.99	$76.99	$76.99	$70.99	$71.99	$72.99	See Web

35

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4393				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
6"	12"	18"	24"	36"	48"	Custom Len.
$90.99	$99.99	$91.99	$91.99	$93.99	$94.99	See Web

36

RG316/U Coax, 50 Ohm

Part No. PE3C4409				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
6"	12"	18"	24"	36"	48"	Custom Len.
$80.99	$82.99	$84.99	$86.99	$89.99	$93.99	See Web

37

SMA FEMALE TO SSMC PLUG RIGHT ANGLE



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4427				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
6"	12"	18"	24"	36"	48"	Custom Len.
$64.99	$68.99	$69.99	$66.99	$66.99	$67.99	See Web

38

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4464				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
6"	12"	18"	24"	36"	48"	Custom Len.
$79.99	$80.99	$80.99	$81.99	$82.99	$83.99	See Web

39

RG316/U Coax, 50 Ohm

Part No. PE3C4410				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
6"	12"	18"	24"	36"	48"	Custom Len.
$76.99	$78.99	$80.99	$81.99	$85.99	$88.99	See Web

40

RG316-DS Coax, 50 Ohm

Part No. PE3C4473				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W
6"	12"	18"	24"	36"	48"	Custom Len.
$74.99	$76.99	$78.99	$79.99	$83.99	$86.99	See Web

41

SMA FEMALE TO SSMC JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4394				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
6"	12"	18"	24"	36"	48"	Custom Len.
$85.99	$94.99	$86.99	$87.99	$88.99	$89.99	See Web

42

SMA FEMALE TO STRAIGHT CUT LEAD SEXLESS



Standard Semi-Rigid Cable Assemblies

PE-020SR Coax, 50 Ohm

Part No. PE3CA1107				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.02" dia.		
3"	6"	9"	12"	-	-	Custom Len.
$74.99	$98.99	Call	$143.99	-	-	See Web

43

PE-034SR Coax, 50 Ohm

Part No. PE3CA1102				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.034" dia.		
3"	6"	9"	12"	-	-	Custom Len.
$40.99	$47.79	$54.99	$61.99	-	-	See Web

44

PE-047SR Coax, 50 Ohm

Part No. PE3CA1103				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.047" dia.		
3"	6"	9"	12"	-	-	Custom Len.
$38.59	$44.99	$51.99	$58.99	-	-	See Web

45

SMA FEMALE TO TNC MALE



Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C3205				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$221.99	$241.99	$261.99	$283.99	$303.99	$233.99	See Web

46

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W00825				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$67.99	$68.99	$69.99	$69.99	$70.99	$67.99	See Web

47

LMR-240 Coax, 50 Ohm

Part No. PE3W00245				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.24" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
Call	Call	Call	Call	Call	Call	See Web

48

SMA FEMALE TO TRIMMED LEAD SEXLESS



Test Probe Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE3C8133				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					36 dB/100ft	32 W
3"	6"	9"	12"	-	-	Custom Len.
$84.99	$84.99	$84.99	$84.99	-	-	See Web

49

PE-SR405FL Coax, 50 Ohm

Part No. PE3C8139				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W
3"	6"	9"	12"	-	-	Custom Len.
$46.39	$46.39	$46.39	$46.39	-	-	See Web

50

PE-SR405FLJ Coax, 50 Ohm


Part No. PE3C8145				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
3"	6"	9"	12"	-	-	Custom Len.
$42.99	$42.99	$42.99	$42.99	-	-	See Web

51

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

SMA FEMALE TO STRAIGHT CUT LEAD SEXLESS



Test Probe Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE3C1057				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	52
3"	6"	9"	12"	-	-	Custom Len.	
$68.99	$68.99	$68.99	$68.99	-	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3C8140				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	53
3"	6"	9"	12"	-	-	Custom Len.	
$46.39	$46.39	$46.39	$46.39	-	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C8146				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	54
3"	6"	9"	12"	-	-	Custom Len.	
$42.99	$42.99	$42.99	$42.99	-	-	See Web	

SMA FEMALE TO TRIMMED LEAD SEXLESS



Standard Semi-Rigid Cable Assemblies

PE-020SR Coax, 50 Ohm

Part No. PE3CA1104					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.02" dia.			55
-	3"	6"	9"	12"	-	Custom Len.		
-	$117.99	$137.99	$157.99	$175.99	-	See Web		

PE-034SR Coax, 50 Ohm

Part No. PE3CA1105					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.034" dia.			56
3"	6"	9"	12"	-	-	Custom Len.		
$46.99	$56.99	$64.99	$72.99	-	-	See Web		

PE-SR047TN Coax, 50 Ohm

Part No. PE3CA1106					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.047" dia.			57
3"	6"	9"	12"	-	-	Custom Len.		
$48.99	$52.99	$58.99	$64.99	-	-	See Web		

SMA FEMALE BULKHEAD TO MCX PLUG RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Precision Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39421						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.							22.5 dB/100ft	130 W	58
6"	9"	12"	18"	24"		-	Custom Len.		
$53.99	$48.79	$53.99	$60.99	$67.99		-	See Web		

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39435						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						0.105" dia.	19.5 dB/100ft	121.5 W	59
6"	9"	12"	18"	24"		-	Custom Len.		
$47.19	$44.59	$47.19	$52.99	$58.99		-	See Web		

SMA FEMALE BULKHEAD TO MMCX PLUG



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE35575						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						0.098" dia.	38 dB/100ft	160 W	60
12"	24"	36"	48"	60"		-	Custom Len.		
$72.99	$76.99	$80.99	$79.99	$82.99		-	See Web		

SMA FEMALE BULKHEAD TO MMCX PLUG RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39436						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						0.098" dia.	19.5 dB/100ft	121.5 W	61
6"	9"	12"	18"	24"		-	Custom Len.		
$71.99	$69.99	$71.99	$77.99	$82.99		-	See Web		

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE34786						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						0.1" dia.	32 dB/100ft	16 W	62
12"	24"	36"	48"	60"		50CM	Custom Len.		
$73.99	$73.99	$74.99	$75.99	$76.99		$73.99	See Web		

RG178B/U Coax, 50 Ohm

Part No. PE3C3821				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	63
12"	24"	36"	48"	60"	50CM	Custom Len.	
$77.99	$76.99	$77.99	$78.99	$80.99	$75.99	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE3W00934				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	64
12"	50CM	24"	36"	100CM	48"	Custom Len.	
$86.99	$88.99	$90.99	$94.99	$95.99	$98.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34686				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	65
12"	24"	36"	48"	60"	-	Custom Len.	
$73.99	$77.99	$81.99	$81.99	$89.99	-	See Web	

Part No. PE3C1081				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	66
12"	50CM	24"	36"	100CM	48"	Custom Len.	
$73.99	$71.99	$72.99	$76.99	$77.99	$80.99	See Web	

SMA FEMALE BULKHEAD TO SMA MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE3468					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						11.88 dB/100ft	450 W	67
6"	12"	18"	24"	36"	48"	Custom Len.		
$72.99	$77.99	$82.99	$82.99	$91.99	$101.99	See Web		

Part No. PE39427					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						12 dB/100ft	400 W	68
6"	9"	12"	18"	24"	-	Custom Len.		
$64.99	$61.99	$64.99	$69.99	Call	-	See Web		

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3W04417					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.161" dia.	11.89 dB/100ft	303.4 W	69
12"	24"	36"	48"	60"	50CM	Custom Len.		
$61.99	$71.99	$82.99	$93.99	$105.99	$67.99	See Web		

Standard Flexible Cable Assemblies

RG316-DS Coax, 50 Ohm

Part No. PE3973					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.114" dia.	30 dB/100ft	85 W	70
6"	12"	18"	24"	36"	48"	Custom Len.		
$65.99	$67.99	$69.99	$71.99	$71.99	$74.99	See Web		

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1038					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.163" dia.			71
12"	24"	36"	50CM	100CM	-	Custom Len.		
$101.99	$125.99	$151.99	Call	$143.99	-	See Web		

SMA FEMALE BULKHEAD TO SMA MALE RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3W05962					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.195" dia.	11.8 dB/100ft		72
12"	24"	36"	48"	60"	50CM	Custom Len.		
$41.99	$42.79	$43.79	$44.59	$45.39	$42.59	See Web		

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39434					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.105" dia.	19.5 dB/100ft	121.5 W	73
6"	9"	12"	18"	24"	-	Custom Len.		
$64.99	$66.99	$66.99	$74.99	$75.99	-	See Web		

SMA FEMALE BULKHEAD TO SMA FEMALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W07334					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.102" dia.	38 dB/100ft		74
12"	24"	36"	48"	60"	50CM	Custom Len.		
$61.99	$65.99	$69.99	$73.99	$77.99	$64.99	See Web		

See Our Website For Current Pricing & Real-Time Stock Availability!

SMA FEMALE BULKHEAD TO SMA FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm — 75

Part No. PE3C5247				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$305.99	$363.99	$353.99	$379.99	$405.99	$317.99	See Web

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm — 76

Part No. PE34709				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W
6"	12"	18"	24"	36"	48"	Custom Len.
$145.99	$149.99	$153.99	$159.99	$167.99	$175.99	See Web

PE-SR401FL Coax, 50 Ohm — 77

Part No. PE3794				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W
6"	12"	18"	24"	36"	48"	Custom Len.
$131.99	$147.99	$149.99	$157.99	$175.99	$193.99	See Web

PE-SR402FL Coax, 50 Ohm — 78

Part No. PE33864				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W
6"	12"	18"	24"	36"	48"	Custom Len.
$87.99	$87.99	$92.99	$97.99	$109.99	$119.99	See Web

PE-SR405FL Coax, 50 Ohm — 79

Part No. PE34070				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W
6"	12"	18"	24"	36"	48"	Custom Len.
$94.99	$94.99	$107.99	$107.99	$119.99	$131.99	See Web

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm — 80

Part No. PE35404				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	-	Custom Len.
$69.99	$70.99	$71.99	$79.99	$73.99	-	See Web

RG174A/U Coax, 50 Ohm — 81

Part No. PE33382				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W
12"	24"	36"	48"	60"	-	Custom Len.
$66.99	$67.99	$67.99	$68.99	$69.99	-	See Web

RG178B/U Coax, 50 Ohm — 82

Part No. PE33084				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
12"	24"	36"	48"	60"	-	Custom Len.
$87.99	$88.99	$95.99	$96.99	$92.99	-	See Web

RG316/U Coax, 50 Ohm — 83

Part No. PE33158				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
$73.99	$81.99	$80.99	$83.99	$87.99	-	See Web

RG316-DS Coax, 50 Ohm — 84

Part No. PE38184				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W
12"	24"	36"	48"	60"	-	Custom Len.
$79.99	$88.99	$86.99	$96.99	$101.99	-	See Web

Standard Semi-Rigid Cable Assemblies

PE-020SR Coax, 50 Ohm — 85

Part No. PE3932				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					85 dB/100ft	2.9 W
6"	12"	18"	24"	36"	48"	Custom Len.
$185.99	$195.99	$207.99	$217.99	$239.99	$259.99	See Web

PE-034SR Coax, 50 Ohm — 86

Part No. PE3520				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					60 dB/100ft	10 W
6"	12"	18"	24"	36"	48"	Custom Len.
$181.99	$187.99	$195.99	$203.99	$217.99	$233.99	See Web

PE-047SR Coax, 50 Ohm — 87

Part No. PE33789				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.047" dia.	40 dB/100ft	32 W
6"	12"	18"	24"	36"	48"	Custom Len.
$163.99	$163.99	$169.99	$175.99	$187.99	$199.99	See Web

PE-SR047AL Coax, 50 Ohm — 88

Part No. PE3929				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W
6"	12"	18"	24"	36"	48"	Custom Len.
$147.99	$151.99	$157.99	$163.99	$173.99	$183.99	See Web

PE-SR401AL-STRAIGHT Coax, 50 Ohm — 89

Part No. PE3764				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	661 W
6"	12"	18"	24"	36"	48"	Custom Len.
$131.99	$143.99	$153.99	$163.99	$185.99	$205.99	See Web

PE-SR402AL Coax, 50 Ohm — 90

Part No. PE3903				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W
6"	12"	18"	24"	36"	48"	Custom Len.
$70.99	$75.99	$81.99	$87.99	$98.99	$109.99	See Web

PE-SR405AL Coax, 50 Ohm — 91

Part No. PE34071				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W
6"	12"	18"	24"	36"	48"	Custom Len.
$89.99	$89.99	$94.99	$101.99	$111.99	$119.99	See Web

RG401/U Coax, 50 Ohm — 92

Part No. PE3634				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W
6"	12"	18"	24"	36"	48"	Custom Len.
$137.99	$149.99	$163.99	$175.99	$201.99	$229.99	See Web

RG402/U Coax, 50 Ohm — 93

Part No. PE33518				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W
6"	12"	18"	24"	36"	48"	Custom Len.
$80.99	$80.99	$85.99	$89.99	$99.99	$109.99	See Web

RG405/U Coax, 50 Ohm — 94

Part No. PE33176				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W
6"	12"	18"	24"	36"	48"	Custom Len.
$90.99	$96.99	$95.99	$99.99	$107.99	$117.99	See Web

SMA FEMALE BULKHEAD TO REVERSE POLARITY SMA MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG141A/U Coax, 50 Ohm — 95

Part No. PE3W02965				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$87.99	$96.99	$105.99	$115.99	$123.99	$93.99	See Web

SMA FEMALE BULKHEAD TO SMB PLUG RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm — 96

Part No. PE3W00135				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$55.99	$56.99	$58.99	$60.99	$61.99	$56.99	See Web

SMA FEMALE BULKHEAD TO SMP FEMALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

PE-P086 Coax, 50 Ohm — 97

Part No. PE3C5233				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.104" dia.	21.7 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$77.99	$86.99	$96.99	$105.99	$115.99	$83.99	See Web

SMA FEMALE BULKHEAD TO SMP FEMALE RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm — 98

Part No. PE3C3937				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$63.99	$62.99	$63.99	$64.99	$65.99	$62.99	See Web

SMA FEMALE BULKHEAD TO SSMC PLUG



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm — 99

Part No. PE3C4428				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
6"	12"	18"	24"	36"	48"	Custom Len.
$62.99	$68.99	$65.99	$68.99	$66.99	$75.99	See Web

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm — 1

Part No. PE3C4448				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	18"	24"	36"	48"	Custom Len.
$71.99	$84.99	$81.99	$85.99	$94.99	$105.99	See Web

See Our Website For Current Pricing & Real-Time Stock Availability!

***Coax Performance at 1 GHz** **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4395				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	2
6"	12"	18"	24"	36"	48"	Custom Len.	
$91.99	$92.99	$84.99	$85.99	$86.99	$87.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4411				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	3
6"	12"	18"	24"	36"	48"	Custom Len.	
$76.99	$82.99	$79.99	$81.99	$90.99	$94.99	See Web	

SMA FEMALE BULKHEAD TO SSMC PLUG RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4429				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		4
6"	12"	18"	24"	36"	48"	Custom Len.	
$58.99	$60.99	$61.99	$63.99	$62.99	$70.99	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4486				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	5
6"	12"	18"	24"	36"	48"	Custom Len.	
$68.99	$79.99	$77.99	$90.99	$91.99	$101.99	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4465				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	6
6"	12"	18"	24"	36"	48"	Custom Len.	
$72.99	$77.99	$74.99	$74.99	$75.99	$77.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4412				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	7
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.99	$77.99	$79.99	$77.99	$80.99	$84.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4474				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	8
6"	12"	18"	24"	36"	48"	Custom Len.	
$78.99	$88.99	$89.99	$83.99	$86.99	$90.99	See Web	

SMA FEMALE BULKHEAD TO SSMC JACK BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4449				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	9
6"	12"	18"	24"	36"	48"	Custom Len.	
$63.99	$68.99	$72.99	$77.99	$86.99	$95.99	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4396				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	10
6"	12"	18"	24"	36"	48"	Custom Len.	
$78.99	$79.99	$79.99	$80.99	$81.99	$82.99	See Web	

SMA FEMALE BULKHEAD TO TNC MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5264				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			11
12"	24"	36"	48"	60"	50CM	Custom Len.	
$283.99	$311.99	$337.99	$363.99	$389.99	$301.99	See Web	

SMA FEMALE BULKHEAD TO TNC MALE RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5265				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			12
12"	24"	36"	48"	60"	50CM	Custom Len.	
$359.99	$311.99	$337.99	$363.99	$389.99	$301.99	See Web	

SMA FEMALE BULKHEAD TO TNC FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5266				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			13
12"	24"	36"	48"	60"	50CM	Custom Len.	
$317.99	$343.99	$371.99	$397.99	$423.99	$335.99	See Web	

SMA FEMALE BULKHEAD TO HMCX32 1.2 PLUG



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1007				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			14
3"	6"	12"	-	-	-	Custom Len.	
$18.19	$16.79	$22.99	-	-	-	See Web	

SMA FEMALE BULKHEAD TO UMCX PLUG RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38299				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	15
3"	6"	9"	12"	18"	24"	Custom Len.	
$83.99	$85.99	$87.99	$89.99	$94.99	$95.99	See Web	

SMA FEMALE BULKHEAD TO UMCX 2.1 PLUG



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1005				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			16
3"	6"	12"	-	-	-	Custom Len.	
$14.39	$16.59	$15.99	-	-	-	See Web	

SMA FEMALE BULKHEAD TO UMCX 2.5 PLUG



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3CA1003				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.07" dia.			17
3"	6"	9"	12"	-	-	Custom Len.	
Call	$16.79	$16.79	$15.59	-	-	See Web	

RG178-DS Coax, 50 Ohm

Part No. PE3CA1004				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.086" dia.			18
3"	6"	12"	-	-	-	Custom Len.	
Call	$17.39	$21.59	-	-	-	See Web	

PE-81mm Coax, 50 Ohm

Part No. PE3CA1000				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			19
3"	6"	12"	-	-	-	Custom Len.	
$16.59	$14.79	$16.59	-	-	-	See Web	

PE-113mm Coax, 50 Ohm

Part No. PE3CA1001				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.044" dia.			20
3"	6"	9"	12"	-	-	Custom Len.	
$20.39	$17.59	$17.79	$17.59	-	-	See Web	

PE-137mm Coax, 50 Ohm

Part No. PE3CA1002				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.053" dia.			21
3"	6"	12"	-	-	-	Custom Len.	
$16.79	$17.59	$16.79	-	-	-	See Web	

SMA FEMALE BULKHEAD TO WMCX 1.6 PLUG



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1006				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			22
3"	10CM	6"	12"	-	-	Custom Len.	
$14.59	Call	$16.79	$16.79	-	-	See Web	

For our complete selection of cable assemblies, please visit our website

REVERSE POLARITY SMA FEMALE BULKHEAD TO SMA MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W04623				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	23
12"	24"	36"	48"	60"	50CM	Custom Len.	
$83.99	$94.99	$105.99	$117.99	$125.99	$90.99	See Web	

REVERSE POLARITY SMA FEMALE BULKHEAD TO SMA MALE RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W04625				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	24
12"	24"	36"	48"	60"	50CM	Custom Len.	
$109.99	$119.99	$129.99	$139.99	$151.99	$115.99	See Web	

REVERSE POLARITY SMA FEMALE BULKHEAD TO HMCX32 1.2 PLUG



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1022				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			25
3"	6"	12"	-	-	-	Custom Len.	
$16.79	$16.79	$18.79	-	-	-	See Web	

REVERSE POLARITY SMA FEMALE BULKHEAD TO UMCX PLUG



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38300				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	26
3"	6"	9"	12"	18"	24"	Custom Len.	
$68.99	Call	$68.99	$68.99	$73.99	$81.99	See Web	

REVERSE POLARITY SMA FEMALE BULKHEAD TO UMCX 2.1 PLUG



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1033				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			27
3"	6"	9"	12"	-	-	Custom Len.	
$16.59	$18.39	Call	$16.59	-	-	See Web	

REVERSE POLARITY SMA FEMALE BULKHEAD TO UMCX 2.5 PLUG



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3CA1019				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.07" dia.			28
3"	6"	9"	12"	-	-	Custom Len.	
Call	$14.59	$15.99	$16.79	-	-	See Web	

RG178-DS Coax, 50 Ohm

Part No. PE3CA1020				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.086" dia.			29
3"	6"	9"	12"	-	-	Custom Len.	
Call	$18.19	$18.19	$15.59	-	-	See Web	

PE-81mm Coax, 50 Ohm

Part No. PE3CA1016				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			30
3"	6"	12"	-	-	-	Custom Len.	
$14.59	$16.79	$15.59	-	-	-	See Web	

PE-113mm Coax, 50 Ohm

Part No. PE3CA1017				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.044" dia.			31
3"	6"	12"	-	-	-	Custom Len.	
$16.79	$16.59	$16.79	-	-	-	See Web	

PE-137mm Coax, 50 Ohm

Part No. PE3CA1018				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.053" dia.			32
3"	6"	12"	-	-	-	Custom Len.	
$16.79	$16.79	$16.79	-	-	-	See Web	

REVERSE POLARITY SMA FEMALE BULKHEAD TO WMCX 1.6 PLUG



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1021				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			33
3"	6"	12"	-	-	-	Custom Len.	
$14.59	$14.59	Call	-	-	-	See Web	

REVERSE THREAD SMA FEMALE BULKHEAD TO UMCX PLUG IGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38301				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	34
3"	6"	9"	12"	18"	24"	Custom Len.	
$73.99	$74.99	$75.99	$76.99	$77.99	$78.99	See Web	

SMA FEMALE 2 HOLE FLANGE TO SMA FEMALE 2 HOLE FLANGE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE35154					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						36 dB/100ft	32 W	35
6"	12"	18"	24"	36"	48"	Custom Len.		
$107.99	$117.99	$111.99	$115.99	$123.99	$131.99	See Web		

PE-SR402FL Coax, 50 Ohm

Part No. PE35108					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						11.88 dB/100ft	450 W	36
6"	12"	18"	24"	36"	48"	Custom Len.		
$94.99	$98.99	$103.99	$107.99	$117.99	$123.99	See Web		

PE-SR405FL Coax, 50 Ohm

Part No. PE35114					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22.5 dB/100ft	130 W	37
6"	12"	18"	24"	36"	48"	Custom Len.		
$83.99	$89.99	$95.99	$103.99	$121.99	$125.99	See Web		

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE35064					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						40 dB/100ft	32 W	38
6"	12"	18"	24"	36"	48"	Custom Len.		
$111.99	$117.99	$117.99	$129.99	$133.99	$145.99	See Web		

RG402/U Coax, 50 Ohm

Part No. PE3525					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						12 dB/100ft	650 W	39
6"	12"	18"	24"	36"	48"	Custom Len.		
$95.99	$101.99	$105.99	$119.99	$117.99	$125.99	See Web		

RG405/U Coax, 50 Ohm

Part No. PE33191					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22 dB/100ft	130 W	40
6"	12"	18"	24"	36"	48"	Custom Len.		
$96.99	$101.99	$96.99	$101.99	$109.99	$117.99	See Web		

SMA FEMALE 2 HOLE FLANGE TO SMP FEMALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE3W05930					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						40 dB/100ft	32 W	41
12"	24"	36"	48"	60"	50CM	Custom Len.		
$97.99	$121.99	$135.99	$147.99	$161.99	$119.99	See Web		

SMA FEMALE 2 HOLE FLANGE TO SMP FEMALE RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W05557					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.105" dia.	19.5 dB/100ft	121.5 W	42
12"	24"	36"	48"	60"	50CM	Custom Len.		
$131.99	$141.99	$151.99	$163.99	$173.99	$137.99	See Web		

See Our Website For Current Pricing & Real-Time Stock Availability!

***Coax Performance at 1 GHz** **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

SMA FEMALE 2 HOLE FLANGE TO STRAIGHT CUT LEAD SEXLESS



SEE MOUNTING HOLE SECTION ON PAGE 419

Test Probe Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE3C0643				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	43
3"	6"	9"	12"	-	-	Custom Len.	
$59.99	$59.99	$59.99	$59.99	-	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3C8142				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	44
3"	6"	9"	12"	-	-	Custom Len.	
$65.99	$65.99	$65.99	$65.99	-	-	See Web	

SMA FEMALE 2 HOLE FLANGE TO TRIMMED LEAD SEXLESS



SEE MOUNTING HOLE SECTION ON PAGE 419

Test Probe Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE3C8134				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					36 dB/100ft	32 W	45
3"	6"	9"	12"	-	-	Custom Len.	
$65.99	$65.99	$65.99	$65.99	-	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3C8141				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	46
3"	6"	9"	12"	-	-	Custom Len.	
$65.99	$65.99	$65.99	$65.99	-	-	See Web	

SMA FEMALE 4 HOLE FLANGE TO BNC FEMALE 4 HOLE FLANGE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Semi-Rigid Cable Assemblies

PE-SR047AL Coax, 50 Ohm

Part No. PE3W08325				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					41 dB/100ft	32 W	47
12"	200CM	-	-	-	-	Custom Len.	
$141.99	$199.99	-	-	-	-	See Web	

SMA FEMALE 4 HOLE FLANGE TO MMCX PLUG RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C0064					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.11" dia.	24 dB/100ft		48
12"	24"	36"	48"	60"	-	Custom Len.		
$125.99	$119.99	$119.99	$121.99	$121.99	-	See Web		

SMA FEMALE 4 HOLE FLANGE TO SMA FEMALE 4 HOLE FLANGE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE35112						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						0.047" dia.	36 dB/100ft	32 W	49
6"	12"	18"	24"	36"	48"	Custom Len.			
$125.99	$125.99	$129.99	$133.99	$143.99	$151.99	See Web			

PE-SR402FL Coax, 50 Ohm

Part No. PE35110						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.							11.88 dB/100ft	450 W	50
6"	12"	18"	24"	36"	48"	Custom Len.			
$113.99	$117.99	$119.99	$125.99	$133.99	$141.99	See Web			

PE-SR405FL Coax, 50 Ohm

Part No. PE35116						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.							22.5 dB/100ft	130 W	51
6"	12"	18"	24"	36"	48"	Custom Len.			
$119.99	$123.99	$123.99	$129.99	$143.99	$155.99	See Web			

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE35118						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.							40 dB/100ft	32 W	52
6"	12"	18"	24"	36"	48"	Custom Len.			
$135.99	$145.99	$151.99	$149.99	$161.99	$173.99	See Web			

RG402/U Coax, 50 Ohm

Part No. PE33502						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.							12 dB/100ft	650 W	53
6"	12"	18"	24"	36"	48"	Custom Len.			
$125.99	$125.99	$129.99	$141.99	$151.99	$161.99	See Web			

RG405/U Coax, 50 Ohm

Part No. PE3223						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.							22 dB/100ft	130 W	54
6"	12"	18"	24"	36"	48"	Custom Len.			
$123.99	$123.99	$135.99	$141.99	$141.99	$149.99	See Web			

SMA FEMALE 4 HOLE FLANGE TO STRAIGHT CUT LEAD SEXLESS



SEE MOUNTING HOLE SECTION ON PAGE 419

Test Probe Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE3C8136				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					36 dB/100ft	32 W	55
3"	6"	9"	12"	-	-	Custom Len.	
$127.99	$127.99	$127.99	$127.99	-	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3C1545				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	56
3"	6"	9"	12"	-	-	Custom Len.	
$70.99	$70.99	$70.99	$70.99	-	-	See Web	

SMA FEMALE 4 HOLE FLANGE TO TRIMMED LEAD SEXLESS



SEE MOUNTING HOLE SECTION ON PAGE 419

Test Probe Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE3C8135				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					36 dB/100ft	32 W	57
3"	6"	9"	12"	-	-	Custom Len.	
$127.99	$127.99	$127.99	$127.99	-	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3C8143				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	58
3"	6"	9"	12"	-	-	Custom Len.	
$73.99	$73.99	$73.99	$73.99	-	-	See Web	

SMB PLUG TO BNC MALE



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3242						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						0.195" dia.	20 dB/100ft	44 W	59
12"	24"	36"	48"	60"	72"	Custom Len.			
$60.99	$60.99	$61.99	$63.99	$64.99	$65.99	See Web			

RG142B/U Coax, 50 Ohm

Part No. PE3349						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						0.195" dia.	13 dB/100ft	650 W	60
12"	24"	36"	48"	60"	72"	Custom Len.			
$59.99	$66.99	$73.99	$81.99	$83.99	$97.99	See Web			

RG174A/U Coax, 50 Ohm

Part No. PE3C3318						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						0.11" dia.	32 dB/100ft	17 W	61
12"	24"	36"	48"	60"	72"	Custom Len.			
$48.19	$48.99	$49.79	$50.99	$51.99	$51.99	See Web			

RG178B/U Coax, 50 Ohm

Part No. PE33825						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						0.072" dia.	44.4 dB/100ft	78 W	62
12"	24"	36"	48"	60"	-	Custom Len.			
$72.99	$74.99	$75.99	$76.99	$78.99	-	See Web			

RG188A/U Coax, 50 Ohm

Part No. PE3C3428						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						0.11" dia.	26 dB/100ft	160 W	63
12"	24"	36"	48"	60"	72"	Custom Len.			
$53.99	$61.99	$59.99	$68.99	$71.99	$74.99	See Web			

RG223/U Coax, 50 Ohm

Part No. PE3236						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						0.209" dia.	13.41 dB/100ft	50 W	64
12"	24"	36"	48"	60"	72"	Custom Len.			
$55.99	$59.99	$62.99	$66.99	$70.99	$74.99	See Web			

PE-P195 Coax, 50 Ohm

Part No. PE37250						Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						0.195" dia.	12.5 dB/100ft	650 W	65
12"	24"	36"	48"	60"	-	Custom Len.			
$66.99	$78.99	$84.99	$95.99	$107.99	-	See Web			

See Our Website For Current Pricing & Real-Time Stock Availability!

SMB PLUG TO N FEMALE



Standard Flexible Cable Assemblies

RG141A/U Coax, 50 Ohm

Part No. PE3W04161				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W	66
12"	24"	36"	48"	60"	50CM	Custom Len.	
$71.99	$80.99	$90.99	$99.99	$109.99	$77.99	See Web	

SMB PLUG TO SMB PLUG



Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE33837				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	67
12"	24"	36"	48"	60"	-	Custom Len.	
$70.99	$82.99	$95.99	$107.99	$119.99	-	See Web	

Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm

Part No. PE34488				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.101" dia.			68
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.99	$75.99	$84.99	$85.99	$94.99	$103.99	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE33650				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	69
12"	24"	36"	48"	60"	72"	Custom Len.	
$71.99	$78.99	$79.99	$74.99	$75.99	$76.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE33652				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	70
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.99	$76.99	$83.99	$83.99	$90.99	$107.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3853				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	71
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.99	$57.99	$57.99	$58.99	$58.99	$59.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE33165				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	72
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.99	$71.99	$72.99	$69.99	$75.99	$77.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3587				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	73
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.99	$66.99	$64.99	$67.99	$69.99	$79.99	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE3721				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	74
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.99	$64.99	$68.99	$73.99	$77.99	$81.99	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE3588				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	75
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.99	$70.99	$76.99	$73.99	$80.99	$77.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3166				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	76
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.99	$73.99	$76.99	$76.99	$79.99	$83.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3915				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	77
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.99	$67.99	$71.99	$75.99	$79.99	$83.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE33704				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	78
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.99	$65.99	$69.99	$70.99	$73.99	$81.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34269				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	79
12"	24"	36"	48"	60"	72"	Custom Len.	
$79.99	$88.99	$89.99	$97.99	$117.99	$115.99	See Web	

SMB PLUG TO SMB PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm

Part No. PE34490				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.101" dia.			80
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.99	$72.99	$81.99	$90.99	$98.99	$107.99	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE33666				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	81
12"	24"	36"	48"	60"	72"	Custom Len.	
$74.99	$75.99	$76.99	$77.99	$78.99	$79.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE33668				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	82
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.99	$73.99	$80.99	$87.99	$93.99	$101.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE33175				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	83
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.99	$70.99	$70.99	$78.99	$79.99	$80.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE33356				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	84
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.99	$79.99	$80.99	$82.99	$83.99	$84.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3592				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	85
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.99	$68.99	$71.99	$73.99	$76.99	$79.99	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE33143				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.118" dia.	30 dB/100ft	160 W	86
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.99	$77.99	$81.99	$85.99	$89.99	$94.99	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE3593				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	87
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.99	$75.99	$77.99	$78.99	$80.99	$81.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE33670				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	88
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.99	$66.99	$75.99	$73.99	$77.99	$81.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE33672				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	89
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.99	$70.99	$74.99	$78.99	$81.99	$85.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34485				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	90
12"	24"	36"	48"	60"	72"	Custom Len.	
$71.99	$75.99	$78.99	$89.99	$86.99	$89.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34481				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	91
12"	24"	36"	48"	60"	72"	Custom Len.	
$83.99	$91.99	$101.99	$109.99	$117.99	$125.99	See Web	

SMB PLUG TO SMB JACK BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE34493				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	92
12"	24"	36"	48"	60"	72"	Custom Len.	
$82.99	$82.99	$83.99	$84.99	$85.99	$86.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE34495				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	93
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.99	$94.99	$92.99	$99.99	$107.99	$113.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE33674				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	94
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.99	$65.99	$62.99	$66.99	$67.99	$63.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

RG178B/U Coax, 50 Ohm

Part No. PE33676	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.072" dia.	44.4 dB/100ft	78 W

12"	24"	36"	48"	60"	72"	Custom Len.
$70.99	$66.99	$67.99	$69.99	$70.99	$77.99	See Web

95

RG188A/U Coax, 50 Ohm

Part No. PE3591	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.11" dia.	26 dB/100ft	160 W

12"	24"	36"	48"	60"	72"	Custom Len.
$58.99	$67.99	$63.99	$66.99	$68.99	$71.99	See Web

96

RG188-DS Coax, 50 Ohm

Part No. PE34489	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.122" dia.	30 dB/100ft	160 W

12"	24"	36"	48"	60"	72"	Custom Len.
$69.99	$73.99	$72.99	$77.99	$81.99	$85.99	See Web

97

RG196A/U Coax, 50 Ohm

Part No. PE3130	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.08" dia.	49 dB/100ft	78 W

12"	24"	36"	48"	60"	72"	Custom Len.
$66.99	$72.99	$70.99	$71.99	$73.99	$75.99	See Web

98

RG223/U Coax, 50 Ohm

Part No. PE34497	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.21" dia.	13.4 dB/100ft	53 W

12"	24"	36"	48"	60"	72"	Custom Len.
$75.99	$79.99	$82.99	$86.99	$89.99	$93.99	See Web

99

RG316-DS Coax, 50 Ohm

Part No. PE34487	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.114" dia.	30 dB/100ft	160 W

12"	24"	36"	48"	60"	72"	Custom Len.
$70.99	$68.99	$71.99	$75.99	$78.99	$82.99	See Web

1

RG400/U Coax, 50 Ohm

Part No. PE34483	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	14.7 dB/100ft	650 W

12"	24"	36"	48"	60"	72"	Custom Len.
$87.99	$96.99	$105.99	$113.99	$121.99	$129.99	See Web

2

PE-B100 Coax, 50 Ohm

Part No. PE34491	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.101" dia.		

12"	24"	36"	48"	60"	72"	Custom Len.
$64.99	$72.99	$81.99	$89.99	$98.99	$107.99	See Web

3

SMB PLUG RIGHT ANGLE TO BNC MALE



Standard Flexible Cable Assemblies

RG223/U Coax, 50 Ohm

Part No. PE3W06905	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.209" dia.	13.41 dB/100ft	50 W

12"	24"	36"	48"	60"	50CM	Custom Len.
$54.99	$58.99	$61.99	$65.99	$69.99	$56.99	See Web

4

SMB PLUG RIGHT ANGLE TO SMA MALE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W03030	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.11" dia.	32 dB/100ft	17 W

12"	24"	36"	48"	60"	50CM	Custom Len.
$47.79	$48.39	$49.19	$49.79	$50.99	$48.19	See Web

5

SMB PLUG RIGHT ANGLE TO SMB PLUG RIGHT ANGLE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE39120	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	11.3 dB/100ft	150 W

12"	24"	36"	48"	60"	-	Custom Len.
$68.99	$69.99	$65.99	$66.99	$66.99	-	See Web

6

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE33654	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	20 dB/100ft	44 W

12"	24"	36"	48"	60"	72"	Custom Len.
$84.99	$79.99	$80.99	$81.99	$82.99	$90.99	See Web

7

RG142B/U Coax, 50 Ohm

Part No. PE33656	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	13 dB/100ft	650 W

12"	24"	36"	48"	60"	72"	Custom Len.
$83.99	$90.99	$103.99	$105.99	$113.99	$125.99	See Web

8

RG174A/U Coax, 50 Ohm

Part No. PE3916	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.11" dia.	32 dB/100ft	17 W

12"	24"	36"	48"	60"	72"	Custom Len.
$79.99	$80.99	$75.99	$75.99	$76.99	$76.99	See Web

9

RG178B/U Coax, 50 Ohm

Part No. PE33350	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.072" dia.	44.4 dB/100ft	78 W

12"	24"	36"	48"	60"	72"	Custom Len.
$81.99	$82.99	$83.99	$84.99	$85.99	$87.99	See Web

10

RG188A/U Coax, 50 Ohm

Part No. PE3589	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.11" dia.	26 dB/100ft	160 W

12"	24"	36"	48"	60"	72"	Custom Len.
$75.99	$86.99	$81.99	$84.99	$86.99	$89.99	See Web

11

RG188-DS Coax, 50 Ohm

Part No. PE34463	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.122" dia.	30 dB/100ft	160 W

12"	24"	36"	48"	60"	72"	Custom Len.
$77.99	$81.99	$85.99	$89.99	$94.99	$98.99	See Web

12

RG196A/U Coax, 50 Ohm

Part No. PE3590	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.08" dia.	49 dB/100ft	78 W

12"	24"	36"	48"	60"	72"	Custom Len.
$76.99	$77.99	$79.99	$81.99	$82.99	$84.99	See Web

13

RG223/U Coax, 50 Ohm

Part No. PE33121	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.209" dia.	13.41 dB/100ft	50 W

12"	24"	36"	48"	60"	72"	Custom Len.
$80.99	$83.99	$87.99	$91.99	$94.99	$98.99	See Web

14

RG316/U Coax, 50 Ohm

Part No. PE3917	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.098" dia.	38 dB/100ft	160 W

12"	24"	36"	48"	60"	72"	Custom Len.
$78.99	$88.99	$85.99	$96.99	$92.99	$105.99	See Web

15

RG316-DS Coax, 50 Ohm

Part No. PE33476	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.114" dia.	30 dB/100ft	160 W

12"	24"	36"	48"	60"	72"	Custom Len.
$82.99	$85.99	$83.99	$86.99	$90.99	$94.99	See Web

16

RG400/U Coax, 50 Ohm

Part No. PE34461	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	14.7 dB/100ft	650 W

12"	24"	36"	48"	60"	72"	Custom Len.
$92.99	$95.99	$105.99	$113.99	$119.99	$129.99	See Web

17

PE-B100 Coax, 50 Ohm

Part No. PE34465	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.101" dia.		

12"	24"	36"	48"	60"	72"	Custom Len.
$75.99	$84.99	$92.99	$101.99	$111.99	$119.99	See Web

18

SMB PLUG RIGHT ANGLE TO SMB JACK BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE34469	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	20 dB/100ft	44 W

12"	24"	36"	48"	60"	72"	Custom Len.
$81.99	$81.99	$82.99	$83.99	$84.99	$85.99	See Web

19

RG142B/U Coax, 50 Ohm

Part No. PE34471	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	13 dB/100ft	650 W

12"	24"	36"	48"	60"	72"	Custom Len.
$82.99	$89.99	$96.99	$103.99	$109.99	$117.99	See Web

20

RG174A/U Coax, 50 Ohm

Part No. PE33261	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.1" dia.	32 dB/100ft	16 W

12"	24"	36"	48"	60"	72"	Custom Len.
$75.99	$75.99	$76.99	$76.99	$77.99	$77.99	See Web

21

RG178B/U Coax, 50 Ohm

Part No. PE34467	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.072" dia.	44.4 dB/100ft	78 W

12"	24"	36"	48"	60"	72"	Custom Len.
$77.99	$71.99	$73.99	$74.99	$75.99	$76.99	See Web

22

See Our Website For Current Pricing & Real-Time Stock Availability!

RG188A/U Coax, 50 Ohm

Part No. PE3594				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	23
12"	24"	36"	48"	60"	72"	Custom Len.	
$75.99	$78.99	$80.99	$83.99	$86.99	$89.99	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE34477				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	24
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.99	$75.99	$79.99	$83.99	$87.99	$91.99	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE33682				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	25
12"	24"	36"	48"	60"	72"	Custom Len.	
$71.99	$73.99	$75.99	$76.99	$78.99	$79.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE34473				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	26
12"	24"	36"	48"	60"	72"	Custom Len.	
$79.99	$82.99	$86.99	$90.99	$93.99	$97.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE33675				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	27
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.99	$74.99	$78.99	$82.99	$85.99	$97.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE33349				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	28
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.99	$80.99	$77.99	$80.99	$84.99	$88.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34475				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	29
12"	24"	36"	48"	60"	72"	Custom Len.	
$99.99	$107.99	$117.99	$123.99	$133.99	$141.99	See Web	

PE-B100 Coax, 50 Ohm

Part No. PE34479				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.101" dia.			30
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.99	$76.99	$85.99	$93.99	$103.99	$111.99	See Web	

SMB PLUG RIGHT ANGLE TO SSMB PLUG



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W04513				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	31
12"	24"	36"	48"	60"	50CM	Custom Len.	
$71.99	$72.99	$72.99	$73.99	$74.99	$71.99	See Web	

SMC PLUG TO 10-32 MALE RIGHT ANGLE



Standard Flexible Cable Assemblies

RG196A/U Coax, 50 Ohm

Part No. PE3W00597				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.		78 W	32
12"	24"	36"	48"	60"	50CM	Custom Len.	
$89.99	$91.99	$93.99	$94.99	$96.99	$90.99	See Web	

SMC PLUG TO BNC MALE



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3244				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	33
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.99	$63.99	$67.99	$64.99	$70.99	$66.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3425				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	34
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.99	$55.99	$56.99	$52.99	$58.99	$53.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3C2578				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	35
12"	24"	36"	48"	60"	72"	Custom Len.	
$51.99	$54.99	$57.99	$60.99	$67.99	$65.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C2599				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	36
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.99	$57.99	$61.99	$65.99	$63.99	$67.99	See Web	

SMC PLUG TO MCX PLUG



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W04152				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		37
12"	24"	36"	48"	60"	127CM	Custom Len.	
$43.99	$44.99	$45.99	$46.79	$47.79	Call	See Web	

SMC PLUG TO SMA MALE



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W04200				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		38
12"	24"	36"	48"	60"	50CM	Custom Len.	
$50.99	$51.99	$52.99	$53.99	$54.99	$51.99	See Web	

SMC PLUG TO SMC PLUG



Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm

Part No. PE34501				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.101" dia.			39
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.99	$68.99	$77.99	$85.99	$94.99	$103.99	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE33641				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	40
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.99	$78.99	$79.99	$80.99	$81.99	$82.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3490				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	41
12"	24"	36"	48"	60"	72"	Custom Len.	
$74.99	$81.99	$88.99	$95.99	$101.99	$109.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3883				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	42
12"	24"	36"	48"	60"	72"	Custom Len.	
$58.99	$63.99	$64.99	$60.99	$60.99	$61.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3902				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	43
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.99	$69.99	$71.99	$78.99	$73.99	$74.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3595				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	44
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.99	$61.99	$64.99	$66.99	$69.99	$72.99	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE33154				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.118" dia.	30 dB/100ft	160 W	45
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.99	$60.99	$63.99	$68.99	$72.99	$76.99	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE3596				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	46
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.99	$66.99	$67.99	$69.99	$71.99	$72.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE33647				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	47
12"	24"	36"	48"	60"	72"	Custom Len.	
$75.99	$79.99	$82.99	$86.99	$89.99	$93.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3808				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	48
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.99	$70.99	$74.99	$78.99	$75.99	$78.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34721				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	49
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.99	$63.99	$67.99	$71.99	$74.99	$83.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

RG400/U Coax, 50 Ohm

Part No. PE34494				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	50
12"	24"	36"	48"	60"	72"	Custom Len.	
$83.99	$92.99	$101.99	$109.99	$119.99	$125.99	See Web	

SMC PLUG TO SMC PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm

Part No. PE34502				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.101" dia.			51
12"	24"	36"	48"	60"	72"	Custom Len.	
$65.99	$74.99	$83.99	$91.99	$101.99	$109.99	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE33658				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	52
12"	24"	36"	48"	60"	72"	Custom Len.	
$82.99	$83.99	$84.99	$85.99	$86.99	$87.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE33660				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	53
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.99	$79.99	$86.99	$92.99	$99.99	$107.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE33556				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	54
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.99	$73.99	$67.99	$67.99	$68.99	$68.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE34492				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	55
12"	24"	36"	48"	60"	72"	Custom Len.	
$75.99	$82.99	$77.99	$79.99	$80.99	$81.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3600				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	56
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.99	$75.99	$86.99	$81.99	$83.99	$86.99	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE34499				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	57
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.99	$73.99	$77.99	$81.99	$85.99	$89.99	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE3601				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	58
12"	24"	36"	48"	60"	72"	Custom Len.	
$71.99	$72.99	$74.99	$76.99	$77.99	$79.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE33664				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	59
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.99	$76.99	$80.99	$84.99	$87.99	$91.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE33363				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	60
12"	24"	36"	48"	60"	72"	Custom Len.	
$82.99	$79.99	$82.99	$86.99	$89.99	$93.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34518				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	26.1 dB/100ft	160 W	61
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.99	$71.99	$75.99	$78.99	$82.99	$85.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34496				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	62
12"	24"	36"	48"	60"	72"	Custom Len.	
$89.99	$97.99	$107.99	$115.99	$123.99	$131.99	See Web	

SMC PLUG TO SMC JACK BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm

Part No. PE34509				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.101" dia.			63
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.99	$72.99	$81.99	$89.99	$98.99	$107.99	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE34503				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	64
12"	24"	36"	48"	60"	72"	Custom Len.	
$82.99	$83.99	$84.99	$85.99	$86.99	$87.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE34505				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	65
12"	24"	36"	48"	60"	72"	Custom Len.	
$81.99	$87.99	$94.99	$101.99	$109.99	$115.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE33580				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	66
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.99	$62.99	$62.99	$62.99	$63.99	$63.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE33352				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	67
12"	24"	36"	48"	60"	72"	Custom Len.	
$85.99	$91.99	$87.99	$88.99	$89.99	$91.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE33686				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	68
12"	24"	36"	48"	60"	72"	Custom Len.	
$58.99	$61.99	$63.99	$66.99	$68.99	$71.99	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE34500				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	69
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.99	$63.99	$67.99	$71.99	$75.99	$80.99	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE33688				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	70
12"	24"	36"	48"	60"	72"	Custom Len.	
$81.99	$83.99	$84.99	$86.99	$88.99	$89.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE34507				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	71
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.99	$81.99	$84.99	$88.99	$92.99	$95.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE33690				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	72
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.99	$62.99	$66.99	$70.99	$74.99	$77.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34511				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	73
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.99	$73.99	$70.99	$81.99	$77.99	$81.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34498				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	74
12"	24"	36"	48"	60"	72"	Custom Len.	
$90.99	$98.99	$107.99	$117.99	$123.99	$131.99	See Web	

SMC PLUG RIGHT ANGLE TO BNC MALE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C1988				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	75
12"	24"	36"	48"	60"	50CM	Custom Len.	
$61.99	$59.99	$60.99	$60.99	$61.99	$59.99	See Web	

SMC PLUG RIGHT ANGLE TO SMC PLUG



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W08322				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	76
12"	60"	100CM	-	-	-	Custom Len.	
$119.99	$155.99	$137.99	-	-	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

SMC PLUG RIGHT ANGLE TO SMC PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm — 77

Part No. PE33643	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	20 dB/100ft	44 W

12"	24"	36"	48"	60"	72"	Custom Len.
$86.99	$87.99	$88.99	$89.99	$99.99	$91.99	See Web

RG142B/U Coax, 50 Ohm — 78

Part No. PE33645	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	13 dB/100ft	650 W

12"	24"	36"	48"	60"	72"	Custom Len.
$77.99	$84.99	$91.99	$98.99	$105.99	$111.99	See Web

RG174A/U Coax, 50 Ohm — 79

Part No. PE3918	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.1" dia.	32 dB/100ft	16 W

12"	24"	36"	48"	60"	72"	Custom Len.
$78.99	$79.99	$80.99	$80.99	$81.99	$88.99	See Web

RG178B/U Coax, 50 Ohm — 80

Part No. PE3765	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.072" dia.	44.4 dB/100ft	78 W

12"	24"	36"	48"	60"	72"	Custom Len.
$80.99	$81.99	$76.99	$77.99	$79.99	$80.99	See Web

RG188A/U Coax, 50 Ohm — 81

Part No. PE3597	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.11" dia.	26 dB/100ft	160 W

12"	24"	36"	48"	60"	72"	Custom Len.
$79.99	$75.99	$78.99	$81.99	$83.99	$86.99	See Web

RG188-DS Coax, 50 Ohm — 82

Part No. PE34464	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.122" dia.	30 dB/100ft	160 W

12"	24"	36"	48"	60"	72"	Custom Len.
$74.99	$78.99	$82.99	$86.99	$91.99	$95.99	See Web

RG196A/U Coax, 50 Ohm — 83

Part No. PE3598	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.08" dia.	49 dB/100ft	78 W

12"	24"	36"	48"	60"	72"	Custom Len.
$69.99	$71.99	$73.99	$74.99	$76.99	$78.99	See Web

RG223/U Coax, 50 Ohm — 84

Part No. PE33649	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.21" dia.	13.4 dB/100ft	53 W

12"	24"	36"	48"	60"	72"	Custom Len.
$74.99	$78.99	$81.99	$85.99	$88.99	$92.99	See Web

RG316/U Coax, 50 Ohm — 85

Part No. PE3919	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.098" dia.	38 dB/100ft	160 W

12"	24"	36"	48"	60"	72"	Custom Len.
$81.99	$85.99	$88.99	$92.99	$96.99	$99.99	See Web

RG316-DS Coax, 50 Ohm — 86

Part No. PE34462	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.114" dia.	26.1 dB/100ft	160 W

12"	24"	36"	48"	60"	72"	Custom Len.
$73.99	$77.99	$80.99	$84.99	$87.99	$91.99	See Web

RG400/U Coax, 50 Ohm — 87

Part No. PE34459	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	14.7 dB/100ft	650 W

12"	24"	36"	48"	60"	72"	Custom Len.
$86.99	$95.99	$105.99	$113.99	$119.99	$129.99	See Web

PE-B100 Coax, 50 Ohm — 88

Part No. PE34466	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.101" dia.		

12"	24"	36"	48"	60"	72"	Custom Len.
$71.99	$80.99	$88.99	$97.99	$105.99	$115.99	See Web

SMC PLUG RIGHT ANGLE TO SMC JACK BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm — 89

Part No. PE34476	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	20 dB/100ft	44 W

12"	24"	36"	48"	60"	72"	Custom Len.
$87.99	$88.99	$89.99	$90.99	$90.99	$91.99	See Web

RG142B/U Coax, 50 Ohm — 90

Part No. PE34478	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	13 dB/100ft	650 W

12"	24"	36"	48"	60"	72"	Custom Len.
$78.99	$85.99	$92.99	$99.99	$107.99	$113.99	See Web

RG174A/U Coax, 50 Ohm — 91

Part No. PE34078	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.1" dia.	32 dB/100ft	16 W

12"	24"	36"	48"	60"	72"	Custom Len.
$69.99	$70.99	$70.99	$71.99	$72.99	$72.99	See Web

RG178B/U Coax, 50 Ohm — 92

Part No. PE34470	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.072" dia.	44.4 dB/100ft	78 W

12"	24"	36"	48"	60"	72"	Custom Len.
$86.99	$87.99	$89.99	$90.99	$91.99	$92.99	See Web

RG188A/U Coax, 50 Ohm — 93

Part No. PE3602	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.11" dia.	26 dB/100ft	160 W

12"	24"	36"	48"	60"	72"	Custom Len.
$71.99	$73.99	$76.99	$79.99	$81.99	$84.99	See Web

RG188-DS Coax, 50 Ohm — 94

Part No. PE34484	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.122" dia.	30 dB/100ft	160 W

12"	24"	36"	48"	60"	72"	Custom Len.
$72.99	$76.99	$80.99	$85.99	$89.99	$93.99	See Web

RG196A/U Coax, 50 Ohm — 95

Part No. PE33692	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.08" dia.	49 dB/100ft	78 W

12"	24"	36"	48"	60"	72"	Custom Len.
$87.99	$89.99	$91.99	$92.99	$94.99	$96.99	See Web

RG223/U Coax, 50 Ohm — 96

Part No. PE34480	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.21" dia.	13.4 dB/100ft	53 W

12"	24"	36"	48"	60"	72"	Custom Len.
$75.99	$79.99	$82.99	$86.99	$90.99	$93.99	See Web

RG316/U Coax, 50 Ohm — 97

Part No. PE34472	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.098" dia.	38 dB/100ft	160 W

12"	24"	36"	48"	60"	72"	Custom Len.
$72.99	$76.99	$79.99	$83.99	$87.99	$91.99	See Web

RG316-DS Coax, 50 Ohm — 98

Part No. PE34474	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.114" dia.	26.1 dB/100ft	160 W

12"	24"	36"	48"	60"	72"	Custom Len.
$71.99	$75.99	$78.99	$82.99	$86.99	$89.99	See Web

RG400/U Coax, 50 Ohm — 99

Part No. PE34482	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.195" dia.	14.7 dB/100ft	650 W

12"	24"	36"	48"	60"	72"	Custom Len.
$95.99	$105.99	$113.99	$119.99	$129.99	$137.99	See Web

PE-B100 Coax, 50 Ohm — 1

Part No. PE34486	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.101" dia.		

12"	24"	36"	48"	60"	72"	Custom Len.
$69.99	$78.99	$86.99	$95.99	$103.99	$113.99	See Web

SMC PLUG RIGHT ANGLE TO TNC FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm — 2

Part No. PE3W05426	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.072" dia.	44.41 dB/100ft	55 W

12"	24"	36"	48"	60"	72"	Custom Len.
$71.99	$72.99	$74.99	$75.99	$77.99	$72.99	See Web

SMC JACK BULKHEAD TO UMCX PLUG RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm — 3

Part No. PE39035	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.072" dia.	44.4 dB/100ft	78 W

3"	6"	9"	12"	18"	24"	Custom Len.
$93.99	$93.99	$93.99	$93.99	$93.99	$94.99	See Web

SMP MALE BULKHEAD TO SMA MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm — 4

Part No. PE3W05498	Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.	0.105" dia.	19.5 dB/100ft	121.5 W

12"	24"	36"	48"	60"	50CM	Custom Len.
$92.99	$103.99	$115.99	$123.99	$135.99	$99.99	See Web

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

SMP MALE BULKHEAD TO SMP FEMALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Semi-Rigid Cable Assemblies

PE-SR405AL Coax, 50 Ohm

Part No. PE3W08323				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	5
36"	60"	-	-	-	-	Custom Len.	
$123.99	$143.99	-	-	-	-	See Web	

SMP FEMALE TO SMA MALE



Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE36162					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						40 dB/100ft	32 W	6
12"	24"	36"	48"	60"	72"	Custom Len.		
$113.99	$125.99	$137.99	$149.99	$165.99	$179.99	See Web		

Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE36168					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22.5 dB/100ft	105 W	7
12"	24"	36"	48"	60"	72"	Custom Len.		
$101.99	$115.99	$127.99	$135.99	$157.99	$161.99	See Web		
Part No. PE3W07044					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22.5 dB/100ft	105 W	8
12"	24"	36"	48"	60"	50CM	Custom Len.		
$61.99	$75.99	$90.99	$105.99	$119.99	$70.99	See Web		

SMP FEMALE TO SMP FEMALE



Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE36148					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.047" dia.	36 dB/100ft	32 W	9
12"	24"	36"	48"	60"	72"	Custom Len.		
$119.99	$121.99	$129.99	$139.99	$147.99	$157.99	See Web		

PE-SR405FL Coax, 50 Ohm

Part No. PE36152					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22.5 dB/100ft	130 W	10
12"	24"	36"	48"	60"	72"	Custom Len.		
$92.99	$105.99	$113.99	$123.99	$135.99	$149.99	See Web		
Part No. PE3C4341					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22.5 dB/100ft	105 W	11
12"	24"	36"	48"	60"	50CM	Custom Len.		
$76.99	$91.99	$105.99	$119.99	$133.99	Call	See Web		

Standard Flexible Cable Assemblies

PE-P047 Coax, 50 Ohm

Part No. PE3C0757					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.056" dia.	35 dB/100ft	43 W	12
12"	24"	36"	48"	60"	50CM	Custom Len.		
$83.99	$90.99	$99.99	$109.99	$119.99	$86.99	See Web		

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE36146					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						40 dB/100ft	32 W	13
12"	24"	36"	48"	60"	72"	Custom Len.		
$123.99	$137.99	$141.99	$153.99	$165.99	$177.99	See Web		

RG405/U Coax, 50 Ohm

Part No. PE36150					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22 dB/100ft	130 W	14
12"	24"	36"	48"	60"	72"	Custom Len.		
$131.99	$141.99	$101.99	$149.99	$117.99	$123.99	See Web		

SMP FEMALE TO SMP FEMALE RIGHT ANGLE



Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE36156					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.047" dia.	36 dB/100ft	32 W	15
12"	24"	36"	48"	60"	72"	Custom Len.		
$113.99	$119.99	$129.99	$137.99	$145.99	$155.99	See Web		

PE-SR405FL Coax, 50 Ohm

Part No. PE36160					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22.5 dB/100ft	130 W	16
12"	24"	36"	48"	60"	72"	Custom Len.		
$107.99	$119.99	$139.99	$143.99	$157.99	$169.99	See Web		

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C0438				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	17
6"	9"	12"	18"	24"	-	Custom Len.	
$98.99	$103.99	$105.99	$103.99	$115.99	-	See Web	
Part No. PE3W08326				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	18
50CM	-	-	-	-	-	Custom Len.	
$67.99	-	-	-	-	-	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE36154					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						40 dB/100ft	32 W	19
12"	24"	36"	48"	60"	72"	Custom Len.		
$117.99	$135.99	$139.99	$151.99	$163.99	$175.99	See Web		

RG405/U Coax, 50 Ohm

Part No. PE36158					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22 dB/100ft	130 W	20
12"	24"	36"	48"	60"	72"	Custom Len.		
$103.99	$111.99	$121.99	$127.99	$135.99	$145.99	See Web		

SMP FEMALE RIGHT ANGLE TO BNC MALE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W06234				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	21
24"	150CM	-	-	-	-	Custom Len.	
$51.99	$53.99	-	-	-	-	See Web	

SMP FEMALE RIGHT ANGLE TO MMCX PLUG RIGHT ANGLE



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C3221					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.098" dia.	19.5 dB/100ft	130 W	22
12"	50CM	24"	36"	100CM	48"	Custom Len.		
$87.99	$89.99	$92.99	$103.99	$105.99	$113.99	See Web		

SMP FEMALE RIGHT ANGLE TO N FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W05673					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.11" dia.	24 dB/100ft		23
12"	24"	36"	48"	60"	50CM	Custom Len.		
$67.99	$68.99	$69.99	$70.99	$71.99	$68.99	See Web		

SMP FEMALE RIGHT ANGLE TO SMA MALE RIGHT ANGLE



Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W05056				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		24
12"	24"	36"	48"	60"	50CM	Custom Len.	
$71.99	$75.99	$79.99	$83.99	$87.99	$74.99	See Web	

SMP FEMALE RIGHT ANGLE TO SMA FEMALE



Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE3W05740					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						22.5 dB/100ft	105 W	25
12"	24"	36"	48"	60"	50CM	Custom Len.		
$85.99	$101.99	$115.99	$127.99	$141.99	$94.99	See Web		

SMP FEMALE RIGHT ANGLE TO SMA FEMALE 2 HOLE FLANGE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE3W05692					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						40 dB/100ft	32 W	26
12"	60"	-	-	-	-	Custom Len.		
$133.99	$179.99	-	-	-	-	See Web		

See Our Website For Current Pricing & Real-Time Stock Availability!

SMP FEMALE RIGHT ANGLE TO SMP FEMALE



Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE3W03777				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	27
12"	24"	36"	48"	60"	50CM	Custom Len.	
$93.99	$107.99	$121.99	$135.99	$149.99	$103.99	See Web	

SMP FEMALE RIGHT ANGLE TO SMP FEMALE RIGHT ANGLE



Standard Flexible Cable Assemblies

PE-P047 Coax, 50 Ohm

Part No. PE3C4969				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.056" dia.	35 dB/100ft	43 W	28
12"	50CM	24"	36"	100CM	48"	Custom Len.	
$127.99	$127.99	$131.99	$141.99	$143.99	$151.99	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE3W04802				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	29
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.99	$83.99	$96.99	$111.99	$121.99	$79.99	See Web	

SMP FEMALE RIGHT ANGLE TO REVERSE POLARITY TNC FEMALE

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W05481				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		30
12"	24"	36"	48"	60"	50CM	Custom Len.	
$105.99	$107.99	$107.99	$109.99	$109.99	$105.99	See Web	

SSMA MALE TO SSMA MALE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3673				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	31
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.99	$80.99	$81.99	$81.99	$82.99	$82.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE33762				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	32
6"	12"	18"	24"	36"	48"	Custom Len.	
$90.99	$90.99	$91.99	$97.99	$93.99	$101.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE33700				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	33
12"	24"	36"	48"	60"	-	Custom Len.	
$76.99	$79.99	$81.99	$84.99	$86.99	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE33071				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		34
6"	12"	18"	24"	36"	48"	Custom Len.	
$90.99	$90.99	$91.99	$93.99	$97.99	$101.99	See Web	

SSMA MALE TO SSMA MALE RIGHT ANGLE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36569				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	35
6"	12"	18"	24"	36"	48"	Custom Len.	
$85.99	$94.99	$85.99	$86.99	$86.99	$87.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36571				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	36
6"	12"	18"	24"	36"	48"	Custom Len.	
$119.99	$119.99	$121.99	$121.99	$121.99	$121.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE36573				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	37
6"	12"	18"	24"	36"	48"	Custom Len.	
$91.99	$87.99	$89.99	$91.99	$95.99	$99.99	See Web	

SSMA MALE RIGHT ANGLE TO SSMA MALE RIGHT ANGLE



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36570				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	38
6"	12"	18"	24"	36"	48"	Custom Len.	
$89.99	$90.99	$90.99	$90.99	$91.99	$91.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36572				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	39
6"	12"	18"	24"	36"	48"	Custom Len.	
$151.99	$151.99	$151.99	$153.99	$153.99	$155.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE36574				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	40
6"	12"	18"	24"	36"	48"	Custom Len.	
$90.99	$92.99	$94.99	$96.99	$101.99	$103.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE38407				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	41
12"	24"	36"	48"	60"	-	Custom Len.	
$85.99	$89.99	$92.99	$95.99	$99.99	-	See Web	

SSMB PLUG TO SMA MALE



Standard Flexible Cable Assemblies

RG188-DS Coax, 50 Ohm

Part No. PE3W06018				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.118" dia.	30 dB/100ft	160 W	42
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.99	$68.99	$72.99	$77.99	$82.99	$66.99	See Web	
Part No. PE3W06717				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.118" dia.	30 dB/100ft	160 W	43
12"	24"	36"	48"	60"	50CM	Custom Len.	
$98.99	$103.99	$107.99	$113.99	$117.99	$101.99	See Web	

SSMB PLUG TO SSMB PLUG



Standard Flexible Cable Assemblies

RG188-DS Coax, 50 Ohm

Part No. PE3W06017				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.118" dia.	30 dB/100ft	160 W	44
12"	24"	36"	48"	60"	50CM	Custom Len.	
$90.99	$95.99	$99.99	$105.99	$109.99	$93.99	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE3122				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	45
12"	24"	36"	48"	60"	72"	Custom Len.	
$94.99	$105.99	$98.99	$101.99	$101.99	$103.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3139				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		46
12"	24"	36"	48"	60"	72"	Custom Len.	
$109.99	$113.99	$109.99	$113.99	$115.99	$119.99	See Web	

SSMB PLUG RIGHT ANGLE TO SSMB PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4801				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	47
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.99	$67.99	$68.99	$69.99	$71.99	$66.99	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE3134				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	48
12"	24"	36"	48"	60"	72"	Custom Len.	
$80.99	$82.99	$84.99	$86.99	$87.99	$89.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3157				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		49
12"	24"	36"	48"	60"	72"	Custom Len.	
$107.99	$111.99	$107.99	$111.99	$123.99	$119.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

SSMC PLUG TO SMB JACK BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3W08023				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	50
12"	18"	150CM	200CM	-	-	Custom Len.	
$79.99	$77.99	$81.99	$84.99	-	-	See Web	

SSMC PLUG TO SSMC PLUG



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4419					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.11" dia.	24 dB/100ft		51
6"	12"	18"	24"	36"	48"		Custom Len.	
$82.99	$91.99	$83.99	$83.99	$84.99	$85.99		See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4441				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	52
6"	12"	18"	24"	36"	48"	Custom Len.	
$87.99	$92.99	$96.99	$101.99	$111.99	$119.99	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4388				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	53
6"	12"	18"	24"	36"	48"	Custom Len.	
$97.99	$97.99	$98.99	$93.99	$94.99	$95.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4403				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	54
6"	12"	18"	24"	36"	48"	Custom Len.	
$88.99	$89.99	$91.99	$93.99	$96.99	$101.99	See Web	

SSMC PLUG TO SSMC PLUG RIGHT ANGLE



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4420					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.11" dia.	24 dB/100ft		55
6"	12"	18"	24"	36"	48"		Custom Len.	
$78.99	$78.99	$79.99	$79.99	$80.99	$81.99		See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4481				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	56
6"	12"	18"	24"	36"	48"	Custom Len.	
$83.99	$88.99	$93.99	$97.99	$107.99	$117.99	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4455				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	57
6"	12"	18"	24"	36"	48"	Custom Len.	
$81.99	$82.99	$82.99	$83.99	$84.99	$85.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4404				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	58
6"	12"	18"	24"	36"	48"	Custom Len.	
$83.99	$90.99	$87.99	$89.99	$92.99	$96.99	See Web	

SSMC PLUG TO SSMC JACK BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4442				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	59
6"	12"	18"	24"	36"	48"	Custom Len.	
$87.99	$92.99	$88.99	$93.99	$103.99	$107.99	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4389				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	60
6"	12"	18"	24"	36"	48"	Custom Len.	
$86.99	$96.99	$88.99	$88.99	$89.99	$101.99	See Web	

SSMC PLUG TO SSMC JACK RIGHT ANGLE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4459				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	61
6"	12"	18"	24"	36"	48"	Custom Len.	
$83.99	$84.99	$85.99	$85.99	$86.99	$87.99	See Web	

SSMC PLUG TO TNC MALE



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4434					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.11" dia.	24 dB/100ft		62
6"	12"	18"	24"	36"	48"		Custom Len.	
$68.99	$69.99	$69.99	$70.99	$71.99	$72.99		See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4453				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	63
6"	12"	18"	24"	36"	48"	Custom Len.	
$73.99	$77.99	$82.99	$87.99	$96.99	$105.99	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4401				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	64
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.99	$80.99	$81.99	$82.99	$83.99	$84.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4417				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	58 dB/100ft	160 W	65
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.99	$82.99	$84.99	$86.99	$89.99	$93.99	See Web	

SSMC PLUG RIGHT ANGLE TO SMA MALE



Standard Flexible Cable Assemblies

RG188-DS Coax, 50 Ohm

Part No. PE3W04994				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.118" dia.	30 dB/100ft	160 W	66
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.99	$77.99	$82.99	$86.99	$91.99	$75.99	See Web	

SSMC PLUG RIGHT ANGLE TO SSMC PLUG RIGHT ANGLE



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4421					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.11" dia.	24 dB/100ft		67
6"	12"	18"	24"	36"	48"		Custom Len.	
$73.99	$74.99	$74.99	$75.99	$76.99	$76.99		See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4482				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	68
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.99	$84.99	$89.99	$93.99	$103.99	$113.99	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4457				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	69
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.99	$71.99	$72.99	$72.99	$73.99	$75.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4374				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		70
6"	12"	18"	24"	36"	48"	Custom Len.	
$79.99	$81.99	$83.99	$84.99	$88.99	$91.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4470				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	71
6"	12"	18"	24"	36"	48"	Custom Len.	
$82.99	$84.99	$81.99	$83.99	$86.99	$90.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

SSMC PLUG RIGHT ANGLE TO SSMC JACK BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4483				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	72
6"	12"	18"	24"	36"	48"	Custom Len.	
$75.99	$80.99	$84.99	$89.99	$98.99	$107.99	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4458				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	73
6"	12"	18"	24"	36"	48"	Custom Len.	
$76.99	$84.99	$77.99	$78.99	$79.99	$80.99	See Web	

SSMC PLUG RIGHT ANGLE TO SSMC JACK RIGHT ANGLE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4460				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	74
6"	12"	18"	24"	36"	48"	Custom Len.	
$73.99	$74.99	$74.99	$75.99	$76.99	$77.99	See Web	

SSMC PLUG RIGHT ANGLE TO TNC MALE



Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4435				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		75
6"	12"	18"	24"	36"	48"	Custom Len.	
$64.99	$71.99	$65.99	$65.99	$66.99	$67.99	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4490				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	76
6"	12"	18"	24"	36"	48"	Custom Len.	
$69.99	$74.99	$78.99	$83.99	$92.99	$101.99	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4468				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	77
6"	12"	18"	24"	36"	48"	Custom Len.	
$69.99	$70.99	$71.99	$71.99	$72.99	$74.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4418				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	58 dB/100ft	160 W	78
6"	12"	18"	24"	36"	48"	Custom Len.	
$76.99	$78.99	$79.99	$81.99	$85.99	$88.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4480				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	79
6"	12"	18"	24"	36"	48"	Custom Len.	
$75.99	$76.99	$78.99	$80.99	$83.99	$87.99	See Web	

SSMC PLUG RIGHT ANGLE TO TNC FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3W05518				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.		55 W	80
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.99	$75.99	$77.99	$78.99	$79.99	$75.99	See Web	

SSMC JACK BULKHEAD TO SSMC JACK BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4443				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	81
6"	12"	18"	24"	36"	48"	Custom Len.	
$70.99	$75.99	$80.99	$84.99	$94.99	$103.99	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4390				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	82
6"	12"	18"	24"	36"	48"	Custom Len.	
$82.99	$82.99	$83.99	$83.99	$84.99	$86.99	See Web	

SSMC JACK BULKHEAD TO SSMC JACK RIGHT ANGLE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4461				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	83
6"	12"	18"	24"	36"	48"	Custom Len.	
$79.99	$79.99	$80.99	$80.99	$81.99	$83.99	See Web	

SSMC JACK BULKHEAD TO TNC MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4454				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	84
6"	12"	18"	24"	36"	48"	Custom Len.	
$64.99	$69.99	$74.99	$78.99	$87.99	$97.99	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4402				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	85
6"	12"	18"	24"	36"	48"	Custom Len.	
$75.99	$76.99	$76.99	$77.99	$78.99	$79.99	See Web	

SSMC JACK RIGHT ANGLE BULKHEAD TO



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4462				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	86
6"	12"	18"	24"	36"	48"	Custom Len.	
$75.99	$84.99	$84.99	$77.99	$78.99	$80.99	See Web	

TNC MALE TO BNC MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE37885				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	87
12"	24"	36"	48"	60"	-	Custom Len.	
$40.19	$40.99	$41.99	$46.39	$47.39	-	See Web	

PE-C200 Coax, 50 Ohm

Part No. PE36068				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10.8 dB/100ft	170 W	88
12"	24"	36"	48"	60"	-	Custom Len.	
$58.99	$63.99	$68.99	$73.99	$78.99	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE37594				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	89
12"	24"	36"	48"	60"	-	Custom Len.	
$53.99	$53.99	$57.99	$61.99	$64.99	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE37563				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	90
12"	24"	36"	48"	60"	-	Custom Len.	
$105.99	$107.99	$109.99	$111.99	$113.99	-	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE34504				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	91
12"	24"	36"	48"	60"	72"	Custom Len.	
$90.99	$94.99	$97.99	$101.99	$105.99	$109.99	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3497				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	92
12"	24"	36"	48"	60"	72"	Custom Len.	
$46.39	$47.39	$48.39	$46.59	$47.39	$51.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

For our complete selection of cable assemblies, please visit our website

RG58-P Coax, 50 Ohm

Part No. PE35789				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.159" dia.	17.3 dB/100ft	632 W	93
12"	24"	36"	48"	60"	-	Custom Len.	
$61.99	$68.99	$74.99	$80.99	$86.99	-	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3551				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	94
12"	24"	36"	48"	60"	72"	Custom Len.	
$50.99	$57.99	$67.99	$71.99	$78.99	$85.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3400				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	95
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.99	$56.99	$57.99	$58.99	$58.99	$59.99	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE39255				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	96
12"	24"	36"	48"	60"	-	Custom Len.	
$82.99	$85.99	$93.99	$101.99	$109.99	-	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3C3401				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	97
12"	24"	36"	48"	60"	72"	Custom Len.	
$57.99	$60.99	$69.99	$65.99	$67.99	$70.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE33969				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	98
12"	24"	36"	48"	60"	72"	Custom Len.	
$89.99	$91.99	$93.99	$95.99	$97.99	$99.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE33701				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	99
12"	24"	36"	48"	60"	72"	Custom Len.	
$101.99	$111.99	$119.99	$127.99	$137.99	$155.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3498				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	1
12"	24"	36"	48"	60"	72"	Custom Len.	
$45.99	$54.99	$58.99	$61.99	$60.99	$69.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C3393				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	2
12"	24"	36"	48"	60"	72"	Custom Len.	
$57.99	$61.99	$68.99	$72.99	$71.99	$75.99	See Web	

RG393/U Coax, 50 Ohm

Part No. PE37859				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W	3
12"	24"	36"	48"	60"	-	Custom Len.	
$94.99	$121.99	$129.99	$147.99	$165.99	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE33535				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	4
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.99	$72.99	$77.99	$91.99	$101.99	$111.99	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE37478				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	5
12"	24"	36"	48"	60"	-	Custom Len.	
$51.99	$61.99	$71.99	$81.99	$91.99	-	See Web	

RG55B/U Coax, 53 Ohm

Part No. PE3904				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	6
12"	24"	36"	48"	60"	72"	Custom Len.	
$47.19	$49.99	$52.99	$55.99	$58.99	$61.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3023				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	7
12"	24"	36"	48"	60"	72"	Custom Len.	
$43.99	$47.99	$49.19	$47.59	$48.79	$53.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE34510				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	8
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.99	$62.99	$65.99	$68.99	$71.99	$74.99	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE34508				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	9
12"	24"	36"	48"	60"	72"	Custom Len.	
$41.39	$42.99	$44.59	$46.39	$47.99	$49.79	See Web	

TNC MALE TO MINI UHF MALE



Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3C0047				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		10
12"	24"	36"	48"	60"	-	Custom Len.	
$38.19	$39.19	$40.19	$40.99	$41.99	-	See Web	

TNC MALE TO N MALE



Standard Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3W01959				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		11
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.99	$55.99	$56.99	$57.99	$58.99	$55.99	See Web	

Low Loss Flexible Cable Assemblies

LMR-240 Coax, 50 Ohm

Part No. PE3W04201				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		12
12"	24"	36"	48"	60"	50CM	Custom Len.	
$50.99	$51.99	$52.99	$53.99	$54.99	$50.99	See Web	

TNC MALE TO SMA MALE



Low Loss Flexible Cable Assemblies

LMR-195-FR Coax, 50 Ohm

Part No. PE3W04028				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		13
12"	24"	36"	48"	60"	50CM	Custom Len.	
$35.59	$50.99	$51.99	$53.99	$54.99	$50.99	See Web	

TNC MALE TO SMA MALE RIGHT ANGLE



Standard Flexible Cable Assemblies

LMR-200 Coax, 50 Ohm

Part No. PE3W07265				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10.5 dB/100ft		14
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.99	$76.99	$77.99	$78.99	$79.99	$76.99	See Web	

TNC MALE TO TNC MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE36555				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	15
12"	24"	36"	48"	60"	-	Custom Len.	
$50.99	$51.99	$47.59	$53.99	$54.99	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE35997				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	16
12"	24"	36"	48"	60"	-	Custom Len.	
$57.99	$55.99	$57.99	$61.99	$63.99	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE35886				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	17
12"	24"	36"	48"	60"	-	Custom Len.	
$117.99	$111.99	$115.99	$123.99	$125.99	-	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5249				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			18
12"	24"	36"	48"	60"	50CM	Custom Len.	
$263.99	$289.99	$315.99	$341.99	$367.99	$279.99	See Web	

LMR-400-DB Coax, 50 Ohm

Part No. PE3W00572				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.15 dB/100ft		19
12"	24"	36"	48"	60"	50CM	Custom Len.	
$99.99	$101.99	$103.99	$105.99	$107.99	$101.99	See Web	

LMR-195 Coax, 50 Ohm

Part No. PE3C0042				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		20
12"	24"	36"	48"	60"	-	Custom Len.	
$45.59	$46.59	$47.59	$48.59	$49.59	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

Part No. PE3C0117				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		21
12"	24"	36"	48"	60"	-	Custom Len.	
$66.99	$67.99	$68.99	$69.99	$67.99	-	See Web	

Precision Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39479				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	22
6"	9"	12"	18"	24"	-	Custom Len.	
$65.99	Call	$70.99	Call	$62.99	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE39471				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	23
6"	9"	12"	18"	24"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE334				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	4.6 dB/100ft		24
12"	24"	36"	48"	60"	50CM	Custom Len.	
$401.99	$433.99	$467.99	$499.99	$535.00	$421.99	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE347				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		25
12"	24"	36"	48"	60"	50CM	Custom Len.	
$199.99	$219.99	$241.99	$261.99	$281.99	$213.99	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34280				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	26
6"	12"	18"	24"	36"	48"	Custom Len.	
$97.99	$103.99	$107.99	$111.99	$119.99	$127.99	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34282				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	27
6"	12"	18"	24"	36"	48"	Custom Len.	
$205.99	$205.99	$215.99	$225.99	$243.99	$261.99	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE3466				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	28
6"	12"	18"	24"	36"	48"	Custom Len.	
$113.99	$113.99	$117.99	$121.99	$137.99	$149.99	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39493				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	29
-	6"	9"	12"	18"	24"	Custom Len.	
-	$70.99	Call	Call	Call	Call	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3684				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	30
6"	12"	18"	24"	36"	48"	Custom Len.	
$101.99	$107.99	$113.99	$119.99	$129.99	$143.99	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39485				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	31
6"	9"	12"	18"	24"	-	Custom Len.	
$62.99	$64.99	$67.99	$72.99	$66.99	-	See Web	

Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm

Part No. PE38830				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.101" dia.			32
12"	24"	36"	48"	60"	-	Custom Len.	
$73.99	$81.99	$89.99	$97.99	$107.99	-	See Web	

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1043				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			33
12"	24"	36"	50CM	100CM	-	Custom Len.	
Call	$365.99	$355.99	Call	Call	-	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE35711				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	34
12"	24"	36"	48"	60"	-	Custom Len.	
$61.99	$70.99	$88.99	$91.99	$101.99	-	See Web	

RG8A/U Coax, 50 Ohm

Part No. PE3418				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	35
12"	24"	36"	48"	60"	72"	Custom Len.	
$83.99	$82.99	$86.99	$89.99	$92.99	$96.99	See Web	

RG8X Coax, 50 Ohm

Part No. PE35671				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13.5 dB/100ft	60 W	36
12"	24"	36"	48"	60"	-	Custom Len.	
$83.99	$88.99	$84.99	$88.99	$91.99	-	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3394				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	37
12"	18"	24"	30"	36"	48"	Custom Len.	
$46.39	$46.79	$47.39	$47.79	$48.39	$49.39	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3544				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	38
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.99	$66.99	$74.99	$81.99	$89.99	$97.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3425				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	39
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.99	$79.99	$84.99	$85.99	$80.99	$81.99	See Web	

Part No. PE3C7891				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	40
12"	24"	36"	48"	60"	50CM	Custom Len.	
$76.99	$77.99	$77.99	$78.99	$79.99	$76.99	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3434				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	41
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.99	$81.99	$84.99	$87.99	$89.99	$92.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3421				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	42
12"	24"	36"	48"	60"	72"	Custom Len.	
$82.99	$84.99	$86.99	$88.99	$90.99	$92.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3435				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	43
12"	24"	36"	48"	60"	72"	Custom Len.	
$111.99	$125.99	$135.99	$145.99	$145.99	$165.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3414				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	44
12"	24"	36"	48"	60"	72"	Custom Len.	
$58.99	$61.99	$65.99	$69.99	$73.99	$77.99	See Web	

RG303/U Coax, 50 Ohm

Part No. PE33013				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.17" dia.	14 dB/100ft	650 W	45
12"	24"	36"	48"	60"	-	Custom Len.	
$52.99	$60.99	$63.99	$70.99	$85.99	-	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34316				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	46
12"	24"	36"	48"	60"	-	Custom Len.	
$72.99	$75.99	$85.99	$82.99	$86.99	-	See Web	

RG393/U Coax, 50 Ohm

Part No. PE33185				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	47
12"	24"	36"	48"	60"	-	Custom Len.	
$119.99	$137.99	$149.99	$179.99	$187.99	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3608				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	48
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.99	$76.99	$88.99	$93.99	$107.99	$117.99	See Web	

LMR-195-FR Coax, 50 Ohm

Part No. PE3W05242				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		49
12"	24"	36"	48"	60"	50CM	Custom Len.	
$32.79	$33.99	$35.19	$36.59	$37.79	$33.59	See Web	

LMR-400-UF Coax, 50 Ohm

Part No. PE3W00808				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	5 dB/100ft		50
12"	24"	36"	48"	60"	50CM	Custom Len.	
$101.99	$105.99	$107.99	$111.99	$113.99	$103.99	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE34273				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	51
6"	12"	18"	24"	36"	48"	Custom Len.	
$99.99	$105.99	$111.99	$117.99	$129.99	$141.99	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE34277				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	52
6"	12"	18"	24"	36"	48"	Custom Len.	
$98.99	$105.99	$109.99	$115.99	$123.99	$135.99	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34275				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	53
6"	12"	18"	24"	36"	48"	Custom Len.	
$187.99	$197.99	$207.99	$219.99	$239.99	$261.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

PE-SR402AL Coax, 50 Ohm

Part No. PE34279				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	54
6"	12"	18"	24"	36"	48"	Custom Len.	
$103.99	$109.99	$115.99	$119.99	$129.99	$141.99	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34284				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	55
6"	12"	18"	24"	36"	48"	Custom Len.	
$98.99	$103.99	$109.99	$115.99	$123.99	$133.99	See Web	

RG401/U Coax, 50 Ohm

Part No. PE34271				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	56
6"	12"	18"	24"	36"	48"	Custom Len.	
$213.99	$227.99	$219.99	$231.99	$259.99	$311.99	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3074				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.1 dB/100ft	450 W	57
6"	12"	18"	24"	36"	48"	Custom Len.	
$115.99	$115.99	$119.99	$123.99	$139.99	$141.99	See Web	

RG405/U Coax, 50 Ohm

Part No. PE33391				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	58
6"	12"	18"	24"	36"	48"	Custom Len.	
$99.99	$103.99	$107.99	$113.99	$121.99	$127.99	See Web	

Standard Flexible Cable Assemblies

RG55B/U Coax, 53 Ohm

Part No. PE3504				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	59
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.99	$58.99	$60.99	$63.99	$66.99	$68.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3402				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	60
12"	18"	24"	30"	36"	48"	Custom Len.	
$46.79	$47.39	$50.99	$48.59	$49.19	$50.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE3430				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	61
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.99	$81.99	$84.99	$87.99	$90.99	$92.99	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE3408				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	62
12"	24"	36"	48"	60"	72"	Custom Len.	
$48.19	$49.99	$55.99	$53.99	$55.99	$56.99	See Web	

TNC MALE TO
TNC MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3C0058				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		63
12"	24"	36"	48"	60"	-	Custom Len.	
$62.99	$63.99	$64.99	$65.99	$66.99	-	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5252				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			64
12"	24"	36"	48"	60"	50CM	Custom Len.	
$337.99	$363.99	$389.99	$417.99	$443.99	$353.99	See Web	

Precision Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39481				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	65
6"	9"	12"	18"	24"	-	Custom Len.	
Call	$54.99	$57.99	$73.99	$71.99	-	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39495				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	66
6"	9"	12"	18"	24"	-	Custom Len.	
$64.99	Call	$64.99	Call	Call	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39487				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	67
6"	9"	12"	18"	24"	-	Custom Len.	
Call	Call	$60.99	$73.99	$74.99	-	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE346				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		68
12"	24"	36"	48"	60"	50CM	Custom Len.	
$305.99	$327.99	$347.99	$367.99	$389.99	$319.99	See Web	

Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE33867				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	69
12"	24"	36"	48"	60"	-	Custom Len.	
$77.99	$85.99	$92.99	$101.99	$109.99	-	See Web	

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1044				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			70
6"	12"	36"	50CM	100CM	-	Custom Len.	
Call	$459.99	Call	Call	Call	-	See Web	

TNC MALE TO
TNC FEMALE



Precision Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39474				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	71
6"	9"	12"	18"	24"	-	Custom Len.	
$56.99	Call	Call	$64.99	$70.99	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39488				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	72
6"	9"	12"	18"	24"	-	Custom Len.	
$56.99	Call	$57.99	$61.99	$66.99	-	See Web	

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39496				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	73
6"	9"	12"	18"	24"	-	Custom Len.	
$57.99	$57.99	$57.99	$65.99	$66.99	-	See Web	

TNC MALE TO
TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3W00780				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		74
12"	24"	36"	48"	60"	50CM	Custom Len.	
$48.99	$48.99	$49.19	$49.19	$49.39	$48.99	See Web	

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3W06580				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	75
12"	24"	36"	48"	60"	50CM	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

Standard Flexible Cable Assemblies

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1046				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			76
12"	24"	36"	50CM	100CM	-	Custom Len.	
$443.99	Call	$437.99	Call	Call	-	See Web	

TNC MALE TO
REVERSE POLARITY TNC MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE37137				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	77
12"	24"	36"	48"	60"	-	Custom Len.	
$43.39	$44.39	$45.19	$50.99	$46.79	-	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE35228				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	78
12"	24"	36"	48"	60"	72"	Custom Len.	
$50.99	$48.39	$49.39	$50.99	$51.99	$55.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE35230				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	79
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.99	$63.99	$70.99	$77.99	$84.99	$91.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE35232				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	80
12"	24"	36"	48"	60"	72"	Custom Len.	
$81.99	$84.99	$86.99	$88.99	$90.99	$92.99	See Web	

For our complete selection of cable assemblies, please visit our website

RG214/U Coax, 50 Ohm

Part No. PE35234				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	81
12"	24"	36"	48"	60"	72"	Custom Len.	
$101.99	$111.99	$129.99	$127.99	$135.99	$145.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE35236				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	82
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.99	$54.99	$57.99	$60.99	$64.99	$72.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE35238				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	83
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.99	$80.99	$84.99	$88.99	$92.99	$95.99	See Web	

REVERSE POLARITY TNC MALE TO BNC MALE



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE35229				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	84
12"	24"	36"	48"	60"	72"	Custom Len.	
$51.99	$52.99	$53.99	$54.99	$55.99	$55.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE35231				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	85
12"	24"	36"	48"	60"	72"	Custom Len.	
$50.99	$57.99	$63.99	$70.99	$78.99	$85.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE35233				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	86
12"	24"	36"	48"	60"	72"	Custom Len.	
$87.99	$90.99	$92.99	$94.99	$96.99	$98.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE34520				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	87
12"	24"	36"	48"	60"	72"	Custom Len.	
$94.99	$103.99	$113.99	$119.99	$129.99	$137.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE35235				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	88
12"	24"	36"	48"	60"	72"	Custom Len.	
$43.19	$46.79	$50.99	$54.99	$57.99	$60.99	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C3414				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	89
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.99	$65.99	$68.99	$72.99	$75.99	$79.99	See Web	

TNC MALE RIGHT ANGLE TO N MALE



Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C1041				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		90
12"	24"	36"	48"	60"	50CM	Custom Len.	
$291.99	$311.99	$315.99	$335.99	$355.99	$287.99	See Web	

TNC MALE RIGHT ANGLE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Low Loss Flexible Cable Assemblies

LMR-240-UF Coax, 50 Ohm

Part No. PE3W09079				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft		91
150CM	-	-	-	-	-	Custom Len.	
$82.99	-	-	-	-	-	See Web	

TNC MALE RIGHT ANGLE TO TNC MALE



Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39473				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	92
6"	9"	12"	18"	24"	-	Custom Len.	
Call	$57.99	Call	Call	Call	-	See Web	

Standard Semi-Rigid Cable Assemblies

PE-SR402AL Coax, 50 Ohm

Part No. PE3W07649				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						450 W	93
12"	24"	36"	48"	60"	50CM	Custom Len.	
$84.99	$96.99	$109.99	$119.99	$131.99	$91.99	See Web	

TNC MALE RIGHT ANGLE TO TNC MALE RIGHT ANGLE



Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C1144				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		94
12"	24"	36"	48"	60"	50CM	Custom Len.	
$415.99	$437.99	$457.99	$477.99	$499.99	$429.99	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5250				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			95
12"	24"	36"	48"	60"	50CM	Custom Len.	
$413.99	$439.99	$465.99	$491.99	$520.00	$429.99	See Web	

Precision Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39472				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	96
6"	9"	12"	18"	24"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39486				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	97
6"	9"	12"	18"	24"	-	Custom Len.	
$79.99	Call	$31.79	Call	Call	-	See Web	

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39480				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	98
6"	9"	12"	18"	24"	-	Custom Len.	
$75.99	Call	Call	Call	$84.99	-	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39494				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	99
6"	9"	12"	18"	24"	-	Custom Len.	
$63.99	$63.99	$63.99	Call	Call	-	See Web	

Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE3194				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		1
12"	24"	36"	48"	-	-	Custom Len.	
$97.99	$105.99	$107.99	$113.99	-	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3W00037				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	2
12"	24"	36"	48"	60"	50CM	Custom Len.	
$115.99	$123.99	$133.99	$141.99	$151.99	$119.99	See Web	

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1045				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			3
12"	24"	36"	50CM	100CM	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

TNC MALE RIGHT ANGLE TO TNC FEMALE



Low Loss Flexible Cable Assemblies

LMR-240 Coax, 50 Ohm

Part No. PE3W06709				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		4
18"	36"	50CM	-	-	-	Custom Len.	
$68.99	$69.99	$68.99	-	-	-	See Web	

TNC MALE RIGHT ANGLE TO TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5254				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			5
12"	24"	36"	48"	60"	50CM	Custom Len.	
$371.99	$391.99	$417.99	$443.99	$469.99	$381.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

***Coax Performance at 1 GHz** **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

TNC FEMALE TO NMO MOUNT SEXLESS



Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37849				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
60"	120"	180"	-	-	-	Custom Len.
$61.99	$66.99	$70.99	-	-	-	See Web

6

TNC FEMALE TO SMA MALE



Standard Flexible Cable Assemblies

RG55B/U Coax, 53 Ohm

Part No. PE3W07646					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.202" dia.		53 W
12"	24"	36"	48"	60"	50CM	Custom Len.	
$53.99	$57.99	$60.99	$63.99	$67.99	$56.99	See Web	

7

TNC FEMALE TO TNC MALE



Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39482					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						12 dB/100ft	400 W
6"	9"	12"	18"	24"	-	Custom Len.	
Call	Call	$57.99	$69.99	$70.99	-	See Web	

8

REVERSE POLARITY TNC FEMALE TO REVERSE POLARITY SMA MALE



Standard Flexible Cable Assemblies

RG55B/U Coax, 53 Ohm

Part No. PE3W07647				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$60.99	$63.99	$67.99	$70.99	$74.99	$62.99	See Web

9

TNC FEMALE BULKHEAD TO MCX PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 419



Precision Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39477					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						22.5 dB/100ft	130 W
6"	9"	12"	15"	18"	24"	Custom Len.	
$22.39	$25.79	$28.99	Call	$81.99	Call	See Web	

10

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39491					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.098" dia.	19.5 dB/100ft	130 W
6"	9"	12"	18"	24"	-	Custom Len.	
$51.99	$52.99	$55.99	$55.99	$60.99	-	See Web	

11

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE33799					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.1" dia.	32 dB/100ft	16 W
12"	24"	36"	48"	60"	-	Custom Len.	
$82.99	$76.99	$77.99	$78.99	$78.99	-	See Web	

12

TNC FEMALE BULKHEAD TO MMCX PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 419



Precision Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39478					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						22.5 dB/100ft	130 W
6"	9"	12"	18"	24"	-	Custom Len.	
$55.99	Call	$61.99	Call	Call	-	See Web	

13

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39492					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.098" dia.	19.5 dB/100ft	130 W
6"	9"	12"	18"	24"	-	Custom Len.	
$52.99	$55.99	$58.99	$62.99	$68.99	-	See Web	

14

Standard Flexible Cable Assemblies

RG188A/U Coax, 50 Ohm

Part No. PE35635				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W
12"	24"	36"	48"	60"	-	Custom Len.
$89.99	$93.99	$96.99	$91.99	$94.99	-	See Web

15

RG316/U Coax, 50 Ohm

Part No. PE3W04293				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$105.99	$109.99	$113.99	$117.99	$121.99	$107.99	See Web

16

TNC FEMALE BULKHEAD TO SMA MALE

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5260					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.16" dia.	11 dB/100ft	560 W
8.500//	12"	24"	36"	48"	60"	Custom Len.	
Call	$295.99	$323.99	$349.99	$375.99	$401.99	See Web	

17

TNC FEMALE BULKHEAD TO SMA MALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W03175					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.105" dia.	19.5 dB/100ft	121.5 W
200CM	-	-	-	-	-	-	Custom Len.
$143.99	-	-	-	-	-	-	See Web

18

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W03417				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$81.99	$82.99	$83.99	$84.99	$84.99	$82.99	See Web

19

RG178B/U Coax, 50 Ohm

Part No. PE3W05425				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$86.99	$87.99	$88.99	$90.99	$91.99	$87.99	See Web

20

Standard Semi-Rigid Cable Assemblies

RG402/U Coax, 50 Ohm

Part No. PE3W10767				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					11.1 dB/100ft	450 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$151.99	$161.99	$169.99	$179.99	$187.99	$147.99	See Web

21

TNC FEMALE BULKHEAD TO SMC PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36779				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W
12"	24"	36"	48"	60"	-	Custom Len.
$96.99	$87.99	$88.99	$88.99	$89.99	-	See Web

22

TNC FEMALE BULKHEAD TO SMP FEMALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE3W05541					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						22.5 dB/100ft	105 W
12"	24"	36"	48"	60"	50CM	Custom Len.	
$137.99	$151.99	$165.99	$179.99	$193.99	$147.99	See Web	

23

Part No. PE3W10030					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						22.5 dB/100ft	105 W
12"	24"	36"	48"	60"	50CM	Custom Len.	
$89.99	$105.99	$119.99	$131.99	$145.99	$84.99	See Web	

24

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

TNC FEMALE BULKHEAD TO SSMC PLUG RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG188A/U Coax, 50 Ohm

Part No. PE3W05752				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	25
12"	24"	36"	48"	60"	50CM	Custom Len.	
$127.99	$143.99	$147.99	$149.99	$153.99	$141.99	See Web	

TNC FEMALE BULKHEAD TO TNC MALE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5253				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.	11 dB/100ft	560 W	26
12"	24"	36"	48"	60"	50CM	Custom Len.	
$295.99	$323.99	$349.99	$375.99	$401.99	$313.99	See Web	

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE348				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		27
12"	24"	36"	48"	60"	50CM	Custom Len.	
$253.99	$275.99	$295.99	$315.99	$337.99	$267.99	See Web	

TNC FEMALE BULKHEAD TO TNC FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C2180				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		28
12"	24"	36"	48"	60"	50CM	Custom Len.	
$301.99	$321.99	$341.99	$363.99	$383.99	$313.99	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5251				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			29
12"	24"	36"	48"	60"	50CM	Custom Len.	
$329.99	$355.99	$383.99	$409.99	$435.99	$347.99	See Web	

TNC FEMALE BULKHEAD TO UMCX PLUG RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38304					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.072" dia.	44.4 dB/100ft	78 W	30
3"	6"	9"	12"	18"	24"	Custom Len.		
$66.99	$68.99	$70.99	$72.99	$73.99	$77.99	See Web		

REVERSE POLARITY TNC FEMALE BULKHEAD TO



SEE MOUNTING HOLE SECTION ON PAGE 419

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W01379				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.			31
12"	24"	36"	48"	60"	50CM	Custom Len.	
$99.99	$101.99	$101.99	$103.99	$103.99	$101.99	See Web	

REVERSE POLARITY TNC FEMALE BULKHEAD TO



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG188A/U Coax, 50 Ohm

Part No. PE3W05762				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	32
12"	24"	36"	48"	60"	50CM	Custom Len.	
$117.99	$121.99	$121.99	$125.99	$129.99	$119.99	See Web	

REVERSE POLARITY TNC FEMALE BULKHEAD TO



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3W05610				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	33
12"	24"	36"	48"	60"	50CM	Custom Len.	
$101.99	$113.99	$123.99	$133.99	$143.99	$109.99	See Web	

REVERSE POLARITY TNC FEMALE BULKHEAD TO



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38303					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.072" dia.			34
3"	6"	9"	12"	18"	24"	Custom Len.		
$66.99	$66.99	$66.99	$69.99	$71.99	$75.99	See Web		

UHF MALE TO BNC MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38674				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	35
12"	24"	36"	48"	60"	-	Custom Len.	
$33.99	$34.79	$35.79	$38.99	$38.19	-	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE34581				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	36
12"	24"	36"	48"	60"	72"	Custom Len.	
$80.99	$83.99	$92.99	$90.99	$94.99	$97.99	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3057				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	37
12"	24"	36"	48"	60"	72"	Custom Len.	
$45.59	$46.59	$47.59	$48.59	$49.59	$50.99	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3898				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	38
12"	24"	36"	48"	60"	72"	Custom Len.	
$44.19	$51.99	$58.99	$65.99	$72.99	$79.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE34583				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	39
12"	24"	36"	48"	60"	72"	Custom Len.	
$82.99	$84.99	$86.99	$88.99	$90.99	$92.99	See Web	

RG214/U Coax, 50 Ohm

Part No. PE33438				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	40
12"	24"	36"	48"	60"	72"	Custom Len.	
$81.99	$90.99	$99.99	$115.99	$119.99	$125.99	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3803				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	41
12"	24"	36"	48"	60"	72"	Custom Len.	
$40.79	$44.39	$47.99	$51.99	$55.99	$58.99	See Web	

RG225/U Coax, 50 Ohm

Part No. PE34589				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	42
12"	24"	36"	48"	60"	72"	Custom Len.	
$121.99	$149.99	$189.99	$229.99	$269.99	$309.99	See Web	

RG393/U Coax, 50 Ohm

Part No. PE34585				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W	43
12"	24"	36"	48"	60"	72"	Custom Len.	
$95.99	$115.99	$133.99	$151.99	$171.99	$189.99	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3231				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	44
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.99	$66.99	$75.99	$79.99	$88.99	$96.99	See Web	

PE-B400 Coax, 50 Ohm

Part No. PE34579				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.403" dia.	6 dB/100ft	190 W	45
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.99	$79.99	$81.99	$83.99	$85.99	$87.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

RG55B/U Coax, 53 Ohm

Part No. PE34591				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W
12"	24"	36"	48"	60"	72"	Custom Len.
$40.79	$43.79	$46.59	$49.39	$52.99	$55.99	See Web

46

RG59B/U Coax, 75 Ohm

Part No. PE3543				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$35.99	$36.99	$38.19	$39.19	$40.39	$41.59	See Web

47

RG62A/U Coax, 93 Ohm

Part No. PE34587				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$39.99	$41.79	$43.59	$48.39	$46.99	$48.79	See Web

48

UHF MALE TO UHF MALE



Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38632				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W
12"	24"	36"	48"	60"	-	Custom Len.
$32.79	$33.59	$34.59	$36.39	$38.19	-	See Web

49

PE-C400 Coax, 50 Ohm

Part No. PE35021				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W
12"	24"	36"	48"	60"	-	Custom Len.
$64.99	$67.99	$73.99	$79.99	$85.99	-	See Web

50

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3623				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W
12"	24"	36"	48"	60"	72"	Custom Len.
$80.99	$78.99	$81.99	$85.99	$89.99	$92.99	See Web

51

RG58C/U Coax, 50 Ohm

Part No. PE3015				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	72"	Custom Len.
$46.39	$47.39	$48.39	$49.59	$50.99	$51.99	See Web

52

RG142B/U Coax, 50 Ohm

Part No. PE33053				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
$46.39	$53.99	$60.99	$64.99	$71.99	-	See Web

53

RG213/U Coax, 50 Ohm

Part No. PE3635				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W
12"	24"	36"	48"	60"	72"	Custom Len.
$70.99	$72.99	$74.99	$76.99	$78.99	$80.99	See Web

54

RG214/U Coax, 50 Ohm

Part No. PE3796				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W
12"	24"	48"	60"	72"	-	Custom Len.
$84.99	$87.99	$105.99	$115.99	$131.99	-	See Web

55

RG223/U Coax, 50 Ohm

Part No. PE3845				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W
12"	24"	36"	48"	60"	72"	Custom Len.
$39.39	$42.99	$46.59	$50.99	$53.99	$57.99	See Web

56

RG393/U Coax, 50 Ohm

Part No. PE33267				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W
12"	24"	36"	48"	60"	72"	Custom Len.
$89.99	$103.99	$129.99	$141.99	$159.99	$179.99	See Web

57

RG400/U Coax, 50 Ohm

Part No. PE3743				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W
12"	24"	36"	48"	60"	-	Custom Len.
$51.99	$60.99	$68.99	$77.99	$85.99	-	See Web

58

RG59B/U Coax, 75 Ohm

Part No. PE3580				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$35.19	$36.19	$37.39	$41.99	$39.59	$40.79	See Web

59

HMCX32 1.2 PLUG TO HMCX32 1.2 PLUG



Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1058					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.032" dia.		
6"	9"	12"	-	-	-	-	Custom Len.
$13.19	$13.99	$14.99	-	-	-	-	See Web

60

UMCX PLUG RIGHT ANGLE TO MCX PLUG



Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38890					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.072" dia.	44.4 dB/100ft	78 W
3"	6"	9"	12"	18"	24"	Custom Len.	
$77.99	$79.99	$77.99	$83.99	$81.99	$86.99	See Web	

61

UMCX PLUG RIGHT ANGLE TO MCX PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38502					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.072" dia.	44.4 dB/100ft	78 W
3"	6"	9"	12"	18"	24"	Custom Len.	
$71.99	$72.99	$71.99	$71.99	$76.99	$80.99	See Web	

62

UMCX PLUG RIGHT ANGLE TO MCX JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Flexible Cable Assemblies

PE-113mm Coax, 50 Ohm

Part No. PE38298					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.045" dia.		
6"	12"	18"	-	-	-	-	Custom Len.
$30.39	$29.59	Call	-	-	-	-	See Web

63

UMCX PLUG RIGHT ANGLE TO REVERSE POLARITY MCX JACK

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38302					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.072" dia.	44.4 dB/100ft	78 W
3"	6"	9"	12"	18"	24"	Custom Len.	
$93.99	$93.99	$93.99	$93.99	$97.99	$103.99	See Web	

64

UMCX PLUG RIGHT ANGLE TO MMCX PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE39078					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.072" dia.	44.4 dB/100ft	78 W
3"	6"	9"	12"	18"	24"	Custom Len.	
$78.99	$80.99	$82.99	$84.99	$89.99	$93.99	See Web	

65

UMCX PLUG RIGHT ANGLE TO SSMB PLUG



Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38930					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.072" dia.	44.4 dB/100ft	78 W
3"	6"	9"	12"	18"	24"	Custom Len.	
$123.99	$123.99	$123.99	$123.99	$127.99	$143.99	See Web	

66

UMCX PLUG RIGHT ANGLE TO STRAIGHT CUT LEAD SEXLESS



Standard Flexible Cable Assemblies

Continued on Next Page

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

RG178B/U Coax, 50 Ohm

Part No. PE38296				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	67
3"	6"	9"	12"	18"	24"	Custom Len.	
$53.99	$35.39	$53.99	$35.39	$40.19	$47.19	See Web	

UMCX 2.1 PLUG TO UMCX 2.1 PLUG



Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1056				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			68
6"	12"	5CM	8CM	9CM	11CM	Custom Len.	
$10.59	$13.59	Call	Call	Call	Call	See Web	

UMCX 2.5 PLUG TO UMCX 2.5 PLUG



Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3CA1054				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.07" dia.			69
6"	9"	12"	-	-	-	Custom Len.	
$13.39	$15.19	$16.79	-	-	-	See Web	

RG178-DS Coax, 50 Ohm

Part No. PE3CA1055				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.086" dia.			70
6"	9"	12"	-	-	-	Custom Len.	
$13.99	$16.79	$21.59	-	-	-	See Web	

PE-113mm Coax, 50 Ohm

Part No. PE3CA1052				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.044" dia.			71
1"	2"	3"	6"	9"	12"	Custom Len.	
Call	Call	Call	$11.59	$11.59	$13.59	See Web	

PE-137mm Coax, 50 Ohm

Part No. PE3CA1053				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.053" dia.			72
6"	9"	12"	-	-	-	Custom Len.	
$12.19	$13.19	$14.19	-	-	-	See Web	

WMCX 1.6 PLUG TO WMCX 1.6 PLUG



Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1057				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			73
6"	9"	12"	-	-	-	Custom Len.	
$11.19	$12.19	$14.39	-	-	-	See Web	

12G SDI 75 OHM 1.0/2.3 MALE TO 75 OHM 1.0/2.3 MALE

AVAILABLE IN MULTIPLE COLOR OPTIONS. SEE TABLE FOR SUFFIX



Standard Flexible Cable Assemblies

4694R Coax, 75 Ohm

Part No. PE3C8746				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.274" dia.			74
12"	36"	72"	120"	300"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

4855R Coax, 75 Ohm

Part No. PE3C8749				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.159" dia.			75
12"	36"	72"	120"	300"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

6G SDI 75 OHM 1.0/2.3 MALE TO 75 OHM 1.0/2.3 MALE

AVAILABLE IN MULTIPLE COLOR OPTIONS. SEE TABLE FOR SUFFIX



Standard Flexible Cable Assemblies

1694A Coax, 75 Ohm

Part No. PE3C8818				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.274" dia.			76
12"	36"	72"	120"	300"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

1855A Coax, 75 Ohm

Part No. PE3C8875				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.159" dia.			77
12"	36"	72"	120"	300"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

75 OHM 1.6/5.6 PLUG TO 75 OHM 1.6/5.6 PLUG



Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE36109				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	78
12"	24"	36"	48"	60"	72"	Custom Len.	
$50.99	$51.99	$52.99	$54.99	$55.99	$56.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE36111				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	79
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.99	$64.99	$67.99	$70.99	$73.99	$75.99	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE36113				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	80
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.99	$74.99	$71.99	$75.99	$79.99	$83.99	See Web	

75 OHM 1.6/5.6 PLUG TO 75 OHM 1.6/5.6 PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

RG179B/U Coax, 75 Ohm

Part No. PE36117				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	81
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.99	$75.99	$78.99	$81.99	$84.99	$87.99	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE36119				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	82
12"	24"	36"	48"	60"	72"	Custom Len.	
$74.99	$78.99	$82.99	$86.99	$91.99	$95.99	See Web	

75 OHM 1.6/5.6 PLUG TO 75 OHM BNC MALE



Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE36127				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	83
12"	24"	36"	48"	60"	72"	Custom Len.	
$49.99	$55.99	$52.99	$53.99	$54.99	$55.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE36129				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	84
12"	24"	36"	48"	60"	72"	Custom Len.	
$58.99	$60.99	$63.99	$66.99	$69.99	$72.99	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE36131				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	85
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.99	$63.99	$67.99	$71.99	$76.99	$80.99	See Web	

75 OHM 1.6/5.6 PLUG RIGHT ANGLE TO 75 OHM 1.6/5.6 PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

RG179B/U Coax, 75 Ohm

Part No. PE36123				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	86
12"	24"	36"	48"	60"	72"	Custom Len.	
$84.99	$87.99	$90.99	$93.99	$96.99	$99.99	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE36125				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	87
12"	24"	36"	48"	60"	72"	Custom Len.	
$86.99	$90.99	$94.99	$98.99	$103.99	$107.99	See Web	

12G SDI 75 OHM BNC MALE TO 75 OHM 1.0/2.3 MALE

AVAILABLE IN MULTIPLE COLOR OPTIONS. SEE TABLE FOR SUFFIX



Standard Flexible Cable Assemblies

4694R Coax, 75 Ohm

Part No. PE3C8743				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.274" dia.			88
12"	36"	72"	120"	300"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

***Coax Performance at 1 GHz** **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

6G SDI 75 OHM BNC MALE TO 75 OHM 1.0/2.3 MALE



AVAILABLE IN MULTIPLE COLOR OPTIONS. SEE TABLE FOR SUFFIX

Standard Flexible Cable Assemblies

1694A Coax, 75 Ohm

Part No. PE3C8815				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.274" dia.			89
12"	36"	72"	120"	300"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

75 OHM BNC MALE TO 75 OHM BNC MALE



Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm

Part No. PE33197				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	100 W	90
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.99	$57.99	$64.99	$63.99	$73.99	$77.99	See Web	

RG6-CATV Coax, 75 Ohm

Part No. PE37808				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.275" dia.	6.55 dB/100ft	6.5 W	91
12"	24"	36"	48"	60"	-	Custom Len.	
$72.99	$73.99	$75.99	$76.99	$71.99	-	See Web	

RG11A/U Coax, 75 Ohm

Part No. PE33399				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W	92
12"	24"	36"	48"	60"	72"	Custom Len.	
$85.99	$87.99	$89.99	$91.99	$93.99	$96.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE33188				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	93
12"	24"	36"	48"	60"	72"	Custom Len.	
$49.59	$50.99	$52.99	$53.99	$54.99	$56.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE33401				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	29.15 dB/100ft		94
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.99	$64.99	$67.99	$71.99	$74.99	$77.99	See Web	

PE-B150 Coax, 75 Ohm

Part No. PE33405				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.15" dia.	20 dB/100ft	25 W	95
12"	24"	36"	48"	60"	72"	Custom Len.	
$71.99	$77.99	$79.99	$74.99	$75.99	$76.99	See Web	

12G SDI 75 OHM BNC MALE TO 75 OHM BNC MALE



AVAILABLE IN MULTIPLE COLOR OPTIONS. SEE TABLE FOR SUFFIX

Standard Flexible Cable Assemblies

4694R Coax, 75 Ohm

Part No. PE3C8741				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.274" dia.			96
12"	36"	72"	120"	300"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

6G SDI 75 OHM BNC MALE TO 75 OHM BNC MALE



AVAILABLE IN MULTIPLE COLOR OPTIONS. SEE TABLE FOR SUFFIX

Standard Flexible Cable Assemblies

1694A Coax, 75 Ohm

Part No. PE3C8813				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.274" dia.			97
12"	36"	72"	120"	300"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

12G SDI 75 OHM BNC MALE TO 75 OHM HD-BNC MALE



AVAILABLE IN MULTIPLE COLOR OPTIONS. SEE TABLE FOR SUFFIX

Standard Flexible Cable Assemblies

4694R Coax, 75 Ohm

Part No. PE3C8742				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.274" dia.			98
12"	36"	72"	120"	300"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

6G SDI 75 OHM BNC MALE TO 75 OHM HD-BNC MALE



AVAILABLE IN MULTIPLE COLOR OPTIONS. SEE TABLE FOR SUFFIX

Standard Flexible Cable Assemblies

1694A Coax, 75 Ohm

Part No. PE3C8814				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.274" dia.			99
12"	36"	72"	120"	300"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

75 OHM BNC MALE TO 75 OHM BNC MALE RIGHT ANGLE



Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm

Part No. PE33407				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	125 W	1
12"	24"	36"	48"	60"	72"	Custom Len.	
$84.99	$88.99	$91.99	$95.99	$98.99	$101.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE33196				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	2
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.99	$69.99	$76.99	$71.99	$73.99	$74.99	See Web	

Part No. PE3W00288				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.		77 W	3
12"	24"	36"	48"	60"	50CM	Custom Len.	
$87.99	$88.99	$90.99	$91.99	$92.99	$88.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE33412				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	4
12"	24"	36"	48"	60"	72"	Custom Len.	
$75.99	$78.99	$78.99	$85.99	$84.99	$87.99	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE33414				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	5
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.99	$82.99	$87.99	$86.99	$90.99	$94.99	See Web	

75 OHM BNC MALE TO 75 OHM BNC FEMALE



Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm

Part No. PE33437				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	125 W	6
12"	24"	36"	48"	60"	72"	Custom Len.	
$99.99	$103.99	$105.99	$109.99	$123.99	$115.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE33443				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	7
12"	24"	36"	48"	60"	72"	Custom Len.	
$65.99	$72.99	$71.99	$74.99	$77.99	$85.99	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE33445				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	8
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.99	$71.99	$75.99	$79.99	$84.99	$88.99	See Web	

75 OHM BNC MALE TO 75 OHM BNC FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm

Part No. PE33417				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	125 W	9
12"	24"	36"	48"	60"	72"	Custom Len.	
$107.99	$111.99	$115.99	$117.99	$121.99	$123.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE33179				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	10
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.99	$75.99	$69.99	$70.99	$71.99	$73.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE33421				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	11
12"	24"	36"	48"	60"	72"	Custom Len.	
$76.99	$79.99	$76.99	$79.99	$82.99	$85.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

PE-B150 Coax, 75 Ohm

Part No. PE33425				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.15" dia.	20 dB/100ft	25 W	12
12"	24"	36"	48"	60"	72"	Custom Len.	
$86.99	$87.99	$88.99	$89.99	$90.99	$91.99	See Web	

12G SDI 75 OHM HD-BNC MALE TO 75 OHM 1.0/2.3 MALE



AVAILABLE IN MULTIPLE COLOR OPTIONS. SEE TABLE FOR SUFFIX

Standard Flexible Cable Assemblies

4694R Coax, 75 Ohm

Part No. PE3C8745				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.274" dia.			13
12"	36"	72"	120"	300"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

4855R Coax, 75 Ohm

Part No. PE3C8748				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.159" dia.			14
12"	36"	72"	120"	300"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

6G SDI 75 OHM HD-BNC MALE TO 75 OHM 1.0/2.3 MALE



AVAILABLE IN MULTIPLE COLOR OPTIONS. SEE TABLE FOR SUFFIX

Standard Flexible Cable Assemblies

1694A Coax, 75 Ohm

Part No. PE3C8817				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.274" dia.			15
12"	36"	72"	120"	300"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

1855A Coax, 75 Ohm

Part No. PE3C8874				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.159" dia.			16
12"	36"	72"	120"	300"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

12G SDI 75 OHM HD-BNC MALE TO 75 OHM HD-BNC MALE



AVAILABLE IN MULTIPLE COLOR OPTIONS. SEE TABLE FOR SUFFIX

Standard Flexible Cable Assemblies

4694R Coax, 75 Ohm

Part No. PE3C8744				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.274" dia.			17
12"	36"	72"	120"	300"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

4855R Coax, 75 Ohm

Part No. PE3C8747				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.159" dia.			18
12"	36"	72"	120"	300"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

6G SDI 75 OHM HD-BNC MALE TO 75 OHM HD-BNC MALE



AVAILABLE IN MULTIPLE COLOR OPTIONS. SEE TABLE FOR SUFFIX

Standard Flexible Cable Assemblies

1694A Coax, 75 Ohm

Part No. PE3C8816				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.274" dia.			19
12"	36"	72"	120"	300"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

1855A Coax, 75 Ohm

Part No. PE3C8873				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.159" dia.			20
12"	36"	72"	120"	300"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

75 OHM BNC MALE RIGHT ANGLE TO 75 OHM BNC MALE RIGHT ANGLE



Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm

Part No. PE33426				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	125 W	21
12"	24"	36"	48"	60"	72"	Custom Len.	
$107.99	$111.99	$113.99	$117.99	$121.99	$123.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE33430				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	22
12"	24"	36"	48"	60"	72"	Custom Len.	
$91.99	$93.99	$101.99	$95.99	$96.99	$97.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE33432				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	29.15 dB/100ft		23
12"	24"	36"	48"	60"	72"	Custom Len.	
$84.99	$87.99	$90.99	$93.99	$96.99	$99.99	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE33434				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	24
12"	24"	36"	48"	60"	72"	Custom Len.	
$86.99	$91.99	$101.99	$99.99	$103.99	$107.99	See Web	

75 OHM BNC FEMALE TO 75 OHM BNC FEMALE



Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm

Part No. PE33448				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	125 W	25
12"	24"	36"	48"	60"	72"	Custom Len.	
$125.99	$129.99	$131.99	$133.99	$135.99	$137.99	See Web	

RG11A/U Coax, 75 Ohm

Part No. PE33450				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W	26
12"	24"	36"	48"	60"	72"	Custom Len.	
$113.99	$115.99	$117.99	$119.99	$121.99	$121.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE33451				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	27
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.99	$69.99	$72.99	$75.99	$78.99	$86.99	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE33456				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	28
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.99	$72.99	$76.99	$80.99	$84.99	$88.99	See Web	

75 OHM BNC FEMALE BULKHEAD TO 75 OHM BNC FEMALE BULKHEAD



SEE MOUNTING HOLE SECTION ON PAGE 419

Standard Flexible Cable Assemblies

RG62A/U Coax, 93 Ohm

Part No. PE3W06444				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.239" dia.	8.7 dB/100ft	77 W	29
12"	24"	36"	48"	60"	50CM	Custom Len.	
$84.99	$87.99	$90.99	$93.99	$96.99	$86.99	See Web	

75 OHM F MALE TO 75 OHM BNC MALE



Standard Flexible Cable Assemblies

RG6-CATV Coax, 75 Ohm

Part No. PE36145				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.275" dia.	6.55 dB/100ft	6.5 W	30
12"	24"	36"	48"	60"	72"	Custom Len.	
$41.39	$42.99	$41.59	$45.99	$47.59	$45.59	See Web	

RG11A/U Coax, 75 Ohm

Part No. PE36147				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W	31
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.99	$69.99	$71.99	$73.99	$75.99	$77.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE36149				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	32
12"	24"	36"	48"	60"	72"	Custom Len.	
$35.99	$34.59	$38.59	$39.99	$41.39	$39.39	See Web	

RG59-WHITE Coax, 75 Ohm

Part No. PE36151				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	8.09 dB/100ft	77 W	33
12"	24"	36"	48"	60"	72"	Custom Len.	
$33.79	$35.99	$38.39	$41.39	$43.79	$46.19	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE36153				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	29.15 dB/100ft		34
12"	24"	36"	48"	60"	72"	Custom Len.	
$49.39	$52.99	$55.99	$54.99	$57.99	$60.99	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE36155				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	35
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.99	$53.99	$58.99	$61.99	$66.99	$70.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

***Coax Performance at 1 GHz** **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

75 OHM F MALE TO 75 OHM F MALE



Low Loss Flexible Cable Assemblies

PE-SF200LL75 Coax, 75 Ohm

Part No. PE3TC1202				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			36
24"	36"	48"	72"	100CM	200CM	Custom Len.	
$111.99	$125.99	$139.99	$167.99	$127.99	$175.99	See Web	

Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm

Part No. PE37163				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	100 W	37
12"	24"	36"	48"	60"	-	Custom Len.	
$21.59	$27.39	$31.99	$35.79	$40.39	-	See Web	

RG6-CATV Coax, 75 Ohm

Part No. PE36132				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.275" dia.	6.55 dB/100ft	6.5 W	38
12"	24"	36"	48"	60"	72"	Custom Len.	
$24.59	$25.99	$27.59	$29.19	$30.79	$31.59	See Web	

RG11A/U Coax, 75 Ohm

Part No. PE36135				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W	39
12"	24"	36"	48"	60"	72"	Custom Len.	
$50.99	$52.99	$58.99	$56.99	$59.99	$61.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE36141				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	40
12"	24"	36"	48"	60"	72"	Custom Len.	
$21.19	$22.39	$23.79	$25.19	$24.79	$25.99	See Web	

RG59-WHITE Coax, 75 Ohm

Part No. PE36143				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	8.09 dB/100ft	77 W	41
12"	24"	36"	48"	60"	72"	Custom Len.	
$21.19	$23.59	$26.19	$28.79	$31.39	$32.99	See Web	

75 OHM F MALE TO 75 OHM F MALE RIGHT ANGLE



Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE38343				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	42
12"	24"	36"	48"	60"	-	Custom Len.	
$27.19	$31.19	$29.59	$30.99	$31.19	-	See Web	

75 OHM F MALE TO 75 OHM F FEMALE



Low Loss Flexible Cable Assemblies

PE-SF200LL75 Coax, 75 Ohm

Part No. PE3TC1203				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			43
24"	36"	48"	72"	100CM	200CM	Custom Len.	
$111.99	$125.99	Call	$167.99	Call	Call	See Web	

75 OHM F MALE TO 75 OHM F FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Flexible Cable Assemblies

RG179B/U Coax, 75 Ohm

Part No. PE3C5570				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft		44
12"	24"	36"	48"	60"	-	Custom Len.	
$33.59	$36.59	$39.59	$42.59	$45.39	-	See Web	

75 OHM F FEMALE TO 75 OHM F FEMALE



Low Loss Flexible Cable Assemblies

PE-SF200LL75 Coax, 75 Ohm

Part No. PE3TC1206				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			45
24"	36"	48"	72"	100CM	200CM	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

75 OHM MINI SMB PLUG TO 75 OHM BNC MALE



Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE34701				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	46
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.99	$60.99	$58.99	$59.99	$63.99	$61.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE34703				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	47
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.99	$69.99	$72.99	$75.99	$74.99	$76.99	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE34705				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	48
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.99	$68.99	$72.99	$82.99	$81.99	$85.99	See Web	

75 OHM MINI SMB PLUG TO 75 OHM MINI SMB PLUG



Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE34681				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	49
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.99	$64.99	$65.99	$66.99	$67.99	$68.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE34683				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	50
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.99	$69.99	$72.99	$75.99	$78.99	$86.99	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE34685				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	51
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.99	$68.99	$72.99	$83.99	$81.99	$85.99	See Web	

75 OHM MINI SMB PLUG TO 75 OHM MINI SMB PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE34687				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	52
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.99	$73.99	$74.99	$75.99	$77.99	$83.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE34689				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	53
12"	24"	36"	48"	60"	72"	Custom Len.	
$81.99	$76.99	$79.99	$82.99	$85.99	$88.99	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE34690				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	54
12"	24"	36"	48"	60"	72"	Custom Len.	
$75.99	$79.99	$84.99	$88.99	$92.99	$96.99	See Web	

75 OHM MINI SMB PLUG RIGHT ANGLE TO

SEE MOUNTING HOLE SECTION ON PAGE 419



Standard Flexible Cable Assemblies

RG187A/U Coax, 75 Ohm

Part No. PE3W07602				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.		200 W	55
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.99	$65.99	$70.99	$75.99	$80.99	$63.99	See Web	

75 OHM MINI SMB PLUG RIGHT ANGLE TO



Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE34692				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	56
12"	24"	36"	48"	60"	72"	Custom Len.	
$89.99	$90.99	$91.99	$92.99	$93.99	$94.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

RG179B/U Coax, 75 Ohm

Part No. PE34694				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	57
12"	24"	36"	48"	60"	72"	Custom Len.	
$93.99	$88.99	$101.99	$94.99	$97.99	$99.99	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE34696				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	58
12"	24"	36"	48"	60"	72"	Custom Len.	
$79.99	$83.99	$87.99	$91.99	$95.99	$99.99	See Web	

75 OHM N MALE TO 75 OHM BNC MALE



Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm

Part No. PE3341				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	125 W	59
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.99	$70.99	$73.99	$76.99	$80.99	$83.99	See Web	

RG11A/U Coax, 75 Ohm

Part No. PE3396				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W	60
12"	24"	36"	48"	60"	72"	Custom Len.	
$82.99	$84.99	$87.99	$89.99	$91.99	$93.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE33605				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	61
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.99	$60.99	$62.99	$68.99	$64.99	$71.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE3398				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	62
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.99	$75.99	$83.99	$86.99	$89.99	$93.99	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE3400				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	63
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.99	$74.99	$78.99	$82.99	$86.99	$90.99	See Web	

75 OHM N MALE TO 75 OHM F MALE



Low Loss Flexible Cable Assemblies

PE-SF200LL75 Coax, 75 Ohm

Part No. PE3TC1205				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			64
24"	36"	48"	72"	100CM	200CM	Custom Len.	
$151.99	$165.99	$185.99	$209.99	$169.99	$217.99	See Web	

Standard Flexible Cable Assemblies

PE-75Test.35 Coax, 75 Ohm

Part No. PE3CA1031				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			65
40CM	60CM	100CM	-	-	-	Custom Len.	
Call	$323.99	Call	-	-	-	See Web	

75 OHM N MALE TO 75 OHM F FEMALE



Low Loss Flexible Cable Assemblies

PE-SF200LL75 Coax, 75 Ohm

Part No. PE3TC1204				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			66
24"	36"	48"	72"	100CM	200CM	Custom Len.	
$151.99	Call	Call	$209.99	$169.99	Call	See Web	

75 OHM N MALE TO 75 OHM N MALE



Low Loss Flexible Cable Assemblies

PE-SF200LL75 Coax, 75 Ohm

Part No. PE3TC1200				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			67
6"	12"	24"	36"	48"	72"	Custom Len.	
Call	Call	$189.99	$217.99	$233.99	$263.99	See Web	

Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm

Part No. PE3612				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	125 W	68
12"	24"	36"	48"	60"	72"	Custom Len.	
$76.99	$79.99	$83.99	$86.99	$89.99	$93.99	See Web	

RG11A/U Coax, 75 Ohm

Part No. PE3616				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8.11 dB/100ft	150 W	69
12"	24"	36"	48"	60"	72"	Custom Len.	
$86.99	$96.99	$98.99	$101.99	$105.99	$97.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3528				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	70
12"	24"	36"	48"	60"	72"	Custom Len.	
$75.99	$80.99	$77.99	$78.99	$84.99	$86.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE3307				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	29.15 dB/100ft		71
12"	24"	36"	48"	60"	72"	Custom Len.	
$87.99	$90.99	$93.99	$96.99	$99.99	$109.99	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE3581				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	72
12"	24"	36"	48"	60"	72"	Custom Len.	
$84.99	$95.99	$92.99	$96.99	$101.99	$105.99	See Web	

PE-75Test.35 Coax, 75 Ohm

Part No. PE3CA1032				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			73
60CM	80CM	90CM	100CM	-	-	Custom Len.	
$367.99	Call	Call	Call	-	-	See Web	

75 OHM N MALE TO 75 OHM N FEMALE



Low Loss Flexible Cable Assemblies

PE-SF200LL75 Coax, 75 Ohm

Part No. PE3TC1201				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			74
24"	36"	48"	72"	100CM	200CM	Custom Len.	
$185.99	$201.99	$215.99	$243.99	Call	$251.99	See Web	

75 OHM N FEMALE TO 75 OHM N FEMALE



Standard Flexible Cable Assemblies

RG11A/U Coax, 75 Ohm

Part No. PE3W04530				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W	75
12"	24"	36"	48"	60"	50CM	Custom Len.	
$109.99	$113.99	$115.99	$117.99	$121.99	$111.99	See Web	

75 OHM SMB PLUG TO 75 OHM BNC MALE



Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE33270				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	76
12"	24"	36"	48"	60"	72"	Custom Len.	
$65.99	$66.99	$67.99	$63.99	$65.99	$66.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE33247				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	77
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.99	$68.99	$77.99	$80.99	$83.99	$87.99	See Web	

PE-B150 Coax, 75 Ohm

Part No. PE33644				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.15" dia.	20 dB/100ft	25 W	78
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.99	$74.99	$75.99	$76.99	$76.99	$77.99	See Web	

75 OHM SMB PLUG TO 75 OHM SMB PLUG



Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE3041				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	79
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.99	$75.99	$76.99	$77.99	$78.99	$79.99	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz **Notes: Cable assembly max frequency may be lower than connector or coax max frequency**

RG179B/U Coax, 75 Ohm

Part No. PE3100				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	29.15 dB/100ft		80
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.99	$75.99	$72.99	$75.99	$78.99	$88.99	See Web	

PE-B150 Coax, 75 Ohm

Part No. PE3112				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.15" dia.	20 dB/100ft	25 W	81
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.99	$73.99	$74.99	$75.99	$76.99	$77.99	See Web	

75 OHM SMC PLUG TO 75 OHM BNC MALE



Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE33330				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	82
12"	24"	36"	48"	60"	72"	Custom Len.	
$57.99	$61.99	$59.99	$61.99	$65.99	$62.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE33586				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	83
12"	24"	36"	48"	60"	72"	Custom Len.	
$74.99	$73.99	$80.99	$78.99	$87.99	$90.99	See Web	

PE-B150 Coax, 75 Ohm

Part No. PE33646				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.15" dia.	20 dB/100ft	25 W	84
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.99	$84.99	$80.99	$81.99	$82.99	$89.99	See Web	

75 OHM SMC PLUG TO 75 OHM SMC PLUG



Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE3362				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	85
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.99	$71.99	$79.99	$73.99	$74.99	$76.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE3376				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	86
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.99	$75.99	$78.99	$81.99	$84.99	$87.99	See Web	

PE-B150 Coax, 75 Ohm

Part No. PE3388				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.15" dia.	20 dB/100ft	25 W	87
12"	24"	36"	48"	60"	72"	Custom Len.	
$89.99	$95.99	$91.99	$92.99	$93.99	$94.99	See Web	

75 OHM TNC MALE TO 75 OHM BNC MALE



Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm

Part No. PE35350				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	125 W	88
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.99	$63.99	$66.99	$70.99	$73.99	$77.99	See Web	

RG11A/U Coax, 75 Ohm

Part No. PE35354				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W	89
12"	24"	36"	48"	60"	72"	Custom Len.	
$101.99	$103.99	$105.99	$107.99	$109.99	$111.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE35358				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	90
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.99	$55.99	$56.99	$57.99	$59.99	$63.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE35362				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	91
12"	24"	36"	48"	60"	72"	Custom Len.	
$71.99	$74.99	$71.99	$74.99	$77.99	$80.99	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE35366				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	92
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.99	$67.99	$71.99	$75.99	$79.99	$83.99	See Web	

75 OHM TNC MALE TO 75 OHM TNC MALE



Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm

Part No. PE35348				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	125 W	93
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.99	$70.99	$73.99	$77.99	$80.99	$83.99	See Web	

RG11A/U Coax, 75 Ohm

Part No. PE35352				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W	94
12"	24"	36"	48"	60"	72"	Custom Len.	
$111.99	$113.99	$115.99	$117.99	$119.99	$121.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE35356				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	95
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.99	$68.99	$69.99	$66.99	$67.99	$73.99	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE35360				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	96
12"	24"	36"	48"	60"	72"	Custom Len.	
$80.99	$77.99	$80.99	$83.99	$86.99	$96.99	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE35364				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	97
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.99	$73.99	$77.99	$81.99	$85.99	$90.99	See Web	

BNC TWINAX PLUG TO BNC TWINAX PLUG



Standard Flexible Cable Assemblies

RG108A/U Coax, 78 Ohm

Part No. PE3480				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.235" dia.	26.2 dB/100ft	30 W	98
18"	36"	60"	90"	120"	180"	Custom Len.	
$95.99	$101.99	$107.99	$137.99	$123.99	$137.99	See Web	

3/4"-20 TWINAX MALE TO 3/4"-20 TWINAX MALE



Standard Flexible Cable Assemblies

PE-S330 Coax, 100 Ohm

Part No. PE3930				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.33" dia.			99
18"	36"	60"	90"	120"	180"	Custom Len.	
$101.99	$105.99	$111.99	$121.99	$127.99	$143.99	See Web	

BANANA PLUG TO SMA MALE



Standard Flexible Cable Assemblies

RG188-DS Coax, 50 Ohm

Part No. PE3W06020				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.118" dia.	30 dB/100ft	160 W	1
12"	24"	36"	48"	60"	50CM	Custom Len.	
$47.19	$51.99	$56.99	$61.99	$65.99	$50.99	See Web	

CIRCULATORS AND ISOLATORS

Circulators

Dual Junction





Connector	Frequency Range (MHz.)	Maximum Power	VSWR Max.	Isolation (dB Min.)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
N	1,000 - 2,000	50 Watt	1.35:1	36	PE83CR1014	$1,730.00	See Web for Volume Pricing	1
	1,700 - 2,200		1.25:1	40	PE83CR1016	$1,030.00		2
	2,000 - 4,000		1.3:1		PE83CR1018	$1,040.00		3
	4,000 - 8,000	10 Watt		36	PE83CR1020	$790.00		4
	7,000 - 12,400	5 Watt		40	PE83CR1022	$735.00		5
SMA	1,000 - 2,000	50 Watt	1.35:1	36	PE83CR1013	$2,040.00		6
	1,700 - 2,200		1.25:1	40	PE83CR1015	$1,070.00		7
	2,000 - 4,000		1.3:1		PE83CR1017	$955.00		8
	4,000 - 8,000	10 Watt		36	PE83CR1019	$995.00		9
	7,000 - 12,400	5 Watt		40	PE83CR1021	$770.00		10
	8,000 - 18,000		1.45:1	32	PE83CR1023	$980.00		11
	11,000 - 18,000		1.25:1	40	PE83CR1024	$950.00		12
	18,000 - 26,500		1.4:1	34	PE83CR1025	$1,070.00		13

Single Junction






Connector	Frequency Range (MHz.)	Maximum Power	VSWR Max.	Isolation (dB Min.)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
2.92mm	18,000 - 26,500	10 Watt	1.8:1	12	PE83CR1027	$1,190.00	See Web for Volume Pricing	14
	22,000 - 33,000		1.7:1	13	PE83CR1028	$1,140.00		15
	26,500 - 40,000		1.8:1	12	PE83CR1032	$1,290.00		16
	32,000 - 36,000			14	PE83CR1029	$1,220.00		17
N	135 - 175	150 Watt	1.3:1	20	PE8427	$1,820.00		18
	330 - 403		1.25:1		PE8429	$1,630.00		19
	380 - 460	1000 Watt			PE8423	$630.00		20
	450 - 520	150 Watt			PE8431	$1,550.00		21
	698 - 960	1000 Watt	1.3:1	18	PE8419	$520.00		22
	1,000 - 2,000	100 Watt	1.35:1		PE83CR1001	$1,410.00		23
	1,000 - 2,000	10 Watt			PE8410	$1,170.00		24
	1,700 - 2,200	100 Watt	1.25:1	20	PE83CR1003	$860.00		25
	1,700 - 2,200	10 Watt		18	PE8415	$535.00		26
	2,000 - 4,000	100 Watt	1.3:1	20	PE83CR1005	$830.00		27
	2,000 - 4,000		1.35:1	18	PE83CR1031	$439.99		28
	2,000 - 4,000	10 Watt	1.3:1		PE8411	$860.00		29
	4,000 - 8,000	50 Watt			PE83CR1007	$705.00		30
	4,000 - 8,000	10 Watt			PE8412	$720.00		31
	7,000 - 12,400	50 Watt	1.25:1	20	PE83CR1009	$560.00		32
	7,000 - 12,400	10 Watt			PE8413	$620.00		33
SMA	135 - 175	150 Watt	1.3:1	20	PE8426	$1,860.00		34
	330 - 403		1.25:1		PE8428	$1,690.00		35
	380 - 460	1000 Watt			PE8422	$640.00		36
	450 - 520	150 Watt			PE8430	$1,550.00		37
	698 - 960	1000 Watt	1.3:1	18	PE8418	$540.00		38
	700 - 800	10 Watt	1.25:1		PE83CR001	$233.99		39
	800 - 960			19	PE83CR007	$297.99		40
	1,000 - 2,000	100 Watt	1.35:1	18	PE83CR1000	$1,410.00		41
	1,000 - 2,000	10 Watt			PE8400	$880.00		42
	1,000 - 2,000			17	PE83CR003	$357.99		43
	1,700 - 2,400		1.3:1		PE83CR004	$229.99		44
	1,700 - 2,200	100 Watt	1.25:1	20	PE83CR1002	$825.00		45
	1,700 - 2,200	10 Watt		18	PE8414	$570.00		46
	2,000 - 4,000	100 Watt	1.3:1	20	PE83CR1004	$845.00		47
	2,000 - 4,000		1.35:1	18	PE83CR1030	$473.99		48

See Our Website For Current Pricing & Real-Time Stock Availability!

Circulators

Single Junction






Connector	Frequency Range (MHz.)	Maximum Power	VSWR Max.	Isolation (dB Min.)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
SMA	2,000 - 4,000	10 Watt	1.3:1	18	PE8401	$600.00	See Web for Volume Pricing	49
	2,000 - 4,000				PE83CR005	$287.99		50
	2,000 - 6,000	25 Watt	1.5:1	14	PE8432	$1,060.00		51
	3,000 - 5,000	10 Watt	1.3:1	18	PE83CR1033	$540.00		52
	4,000 - 8,000	80 Watt	1.4:1	17	PE83CR1034	$495.99		53
	4,000 - 8,000	50 Watt	1.3:1	18	PE83CR1006	$745.00		54
	4,000 - 8,000	10 Watt			PE8402	$373.99		55
	4,000 - 8,000		1.35:1	17	PE83CR006	$287.99		56
	6,000 - 18,000		1.5:1	14	PE8433	$985.00		57
	7,000 - 12,400	50 Watt	1.25:1	20	PE83CR1008	$565.00		58
	7,000 - 12,400	10 Watt	1.3:1	18	PE83CR000	$239.99		59
	7,000 - 12,400				PE8403	$345.99		60
	8,000 - 12,000		1.5:1		PE83CR1026	$615.00		61
	8,000 - 18,000	50 Watt	1.45:1	16	PE83CR1010	$565.00		62
	8,000 - 18,000	10 Watt			PE8404	$417.99		63
	8,000 - 18,000		1.55:1	13	PE83CR002	$357.99		64
	11,000 - 18,000	50 Watt	1.25:1	20	PE83CR1011	$615.00		65
	11,000 - 18,000	10 Watt			PE8405	$459.99		66
	18,000 - 26,500	50 Watt	1.4:1	17	PE83CR1012	$635.00		67
	18,000 - 26,500	10 Watt			PE8406	$485.99		68

Isolators

Dual Junction






Connector	Frequency Range (MHz.)	Maximum Power	VSWR Max.	Isolation (dB Min.)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
N	1,000 - 2,000	50 Watt	1.35:1	36	PE83IR1014	$1,770.00	See Web for Volume Pricing	69
	1,700 - 2,200		1.25:1	40	PE83IR1016	Call		70
	2,000 - 4,000		1.3:1		PE83IR1018	$995.00		71
	4,000 - 8,000	10 Watt		36	PE83IR1020	$840.00		72
	7,000 - 12,400	5 Watt	1.25:1	40	PE83IR1022	Call		73
SMA	1,000 - 2,000	50 Watt	1.35:1	36	PE83IR1013	$1,770.00		74
	1,700 - 2,200		1.25:1	40	PE83IR1015	$1,080.00		75
	2,000 - 4,000		1.3:1		PE83IR1017	$1,050.00		76
	4,000 - 8,000	10 Watt		36	PE83IR1019	$940.00		77
	7,000 - 12,400	5 Watt	1.25:1	40	PE83IR1021	$1,060.00		78
	8,000 - 18,000		1.45:1	32	PE83IR1023	$1,030.00		79
	11,000 - 18,000		1.25:1	40	PE83IR1024	$955.00		80
	18,000 - 26,500		1.4:1	34	PE83IR1025	$1,100.00		81

Single Junction




Connector	Frequency Range (MHz.)	Maximum Power	VSWR Max.	Isolation (dB Min.)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
2.4mm	35,000 - 42,500	10 Watt	1.6:1	14	PE83IR1038	$1,220.00	See Web for Volume Pricing	82
2.92mm	18,000 - 26,500	10 Watt	1.7:1	14	PE83IR1033	$945.00		83
	18,000 - 26,500				PE83IR1041	$2,050.00		84
	22,000 - 33,000		1.8:1	13	PE83IR1035	$960.00		85
	26,500 - 40,000	5 Watt	1.5:1	14	PE8320	$1,420.00		86

See Our Website For Current Pricing & Real-Time Stock Availability!

Isolators

Single Junction








Connector	Frequency Range (MHz.)	Maximum Power	VSWR Max.	Isolation (dB Min.)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
2.92mm	26,500 - 40,000	10 Watt	1.7:1	12	PE83IR1036	$945.00	See Web for Volume Pricing	87
	26,500 - 40,000				PE83IR1037	$945.00		88
	27,000 - 31,000	5 Watt	1.25:1	20	PE8319	$1,290.00		89
N	135 - 175	150 Watt	1.3:1	20	PE8322	$1,900.00		90
	330 - 403		1.25:1		PE8324	$1,300.00		91
	380 - 460	100 Watt			PE8425	$675.00		92
	450 - 520	150 Watt			PE8326	$1,230.00		93
	698 - 960	1000 Watt	1.3:1	18	PE8421	$585.00		94
	1,000 - 2,000	10 Watt	1.35:1		PE8310	$1,280.00		95
	1,000 - 2,000			17	PE83IR003	$499.99		96
	1,000 - 2,000	100 Watt		18	PE83IR1001	$1,610.00		97
	1,700 - 2,200		1.25:1	20	PE83IR1003	$915.00		98
	1,700 - 2,200	10 Watt		18	PE8417	$323.99		99
	2,000 - 4,000		1.3:1		PE8311	$880.00		1
	2,000 - 4,000	100 Watt		20	PE83IR1005	$870.00		2
	4,000 - 8,000	10 Watt		18	PE8312	$750.00		3
	4,000 - 8,000	50 Watt			PE83IR1007	$765.00		4
	7,000 - 12,400	10 Watt	1.25:1	20	PE8313	$950.00		5
SMA	135 - 175	150 Watt	1.3:1	20	PE8321	$2,150.00		6
	330 - 403		1.25:1		PE8323	$1,760.00		7
	380 - 460	100 Watt			PE8424	$685.00		8
	450 - 520	150 Watt			PE8325	$1,620.00		9
	698 - 960	1000 Watt	1.3:1	18	PE8420	$870.00		10
	800 - 900	100 Watt	1.25:1	20	PE83IR007	$283.99		11
	1,000 - 2,000	10 Watt	1.5:1	16	PE83IR1032	$825.00		12
	1,000 - 2,000		1.4:1	17	PE83IR002	$393.99		13
	1,000 - 2,000		1.35:1	18	PE8300	$890.00		14
	1,000 - 2,000	100 Watt			PE83IR1000	$1,500.00		15
	1,700 - 2,200	10 Watt	1.25:1		PE8416	$590.00		16
	1,700 - 2,200	100 Watt		20	PE83IR1002	$930.00		17
	1,700 - 2,400	10 Watt	1.35:1	18	PE83IR004	$275.99		18
	2,000 - 4,000		1.3:1		PE8301	$725.00		19
	2,000 - 4,000		1.4:1		PE83IR005	$383.99		20
	2,000 - 4,000	100 Watt	1.3:1	20	PE83IR1004	$865.00		21
	2,000 - 6,000	10 Watt	1.8:1	12	PE83IR1039	$560.00		22
	2,000 - 6,000	20 Watt	1.5:1	14	PE8327	$1,240.00		23
	2,000 - 8,000	10 Watt	1.35:1	15	PE8316	$1,630.00		24
	2,000 - 10,000			13	PE8317	$1,630.00		25
	3,500 - 12,800	2 Watt	1.5:1	17	PE8314	$1,610.00		26
	4,000 - 8,000	10 Watt	1.3:1	18	PE8302	$415.99		27
	4,000 - 8,000		1.35:1		PE83IR006	$379.99		28
	4,000 - 8,000	30 Watt		19	PE83IR1040	$570.00		29
	4,000 - 8,000	50 Watt	1.3:1	18	PE83IR1006	$635.00		30
	6,000 - 18,000	10 Watt	1.6:1	10	PE83IR1029	$575.00		31
	6,000 - 18,000				PE83IR1030	$635.00		32
	6,000 - 18,000				PE83IR1031	$575.00		33
	6,000 - 18,000		1.5:1	14	PE8328	$1,270.00		34
	4,000 - 18,000			15	PE8315	$1,570.00		35
	7,000 - 12,400	1 Watt	1.3:1	18	PE8303	$367.99		36
	7,000 - 12,400	10 Watt			PE83IR000	$359.99		37
	8,000 - 18,000	1 Watt	1.45:1	16	PE8304	$389.99		38
	8,000 - 18,000	10 Watt	1.5:1		PE83IR001	$351.99		39
	8,000 - 18,000	50 Watt	1.45:1		PE83IR1010A	$580.00		40
	8,000 - 12,000	10 Watt	1.35:1	20	PE83IR1026	$489.99		41
	8,000 - 12,000				PE83IR1027	$489.99		42
	11,000 - 18,000	1 Watt	1.25:1		PE8305	$357.99		43
	11,000 - 18,000	50 Watt			PE83IR1011	$610.00		44
	12,000 - 18,000	10 Watt	1.35:1		PE83IR1028	$530.00		45
	17,300 - 22,000		1.25:1		PE8318	$705.00		46
	18,000 - 26,500	1 Watt	1.4:1	17	PE8306	$359.99		47
	18,000 - 26,500	10 Watt	1.7:1	14	PE83IR1034	$930.00		48
	18,000 - 26,500	50 Watt	1.4:1	17	PE83IR1012	$790.00		49

See Our Website For Current Pricing & Real-Time Stock Availability!

INDEX GUIDE TO
COAXIAL CABLES



COAXIAL CABLES.....227

75 OHM BROADCAST**.....228**



Pasternack's selection of 75 Ohm Broadcast coaxial cable includes RG59-P plenum cable, commercial grade RG6-CATV, HD mini 59 cable in multiple colors as well as PTFE jacketed RG187A/U.

RG MIL-C-17 TYPE CABLE**.....230**



Pasternack offers 31 different MIL-C-17 compliant coaxial cable types. These cables are available in various diameters, jacket materials, impedances, and velocity factors, providing numerous RF cable options to fit your specific requirements.


COMMUNICATIONS**.....228**

Our selection of Low Loss cable is designed with high Velocity Factor (VF) dielectric materials and two outer shields for communications applications requiring Low Loss and High Isolation. These cables are offered in several popular sizes including 0.195", 0.240", 0.400", and 0.600" diameters.



SEMIRIGID AND FORMABLE**.....231**

Pasternack's Precision Cables are designed for RF and Microwave applications with frequencies up to 65 GHz. These cables are constructed of copper jacketed and tinned aluminum semirigid designs; and tinned braid conformable cable in both FEP jacketed and unjacketed designs. The semi rigid and conformable cables are available from 0.020 to 0.250 inches in diameter.



HIGH PERFORMANCE**.....230**



Pasternack's line of High Performance Flexible Cable has high Velocity Factors of 70 to 85% and incorporate Spiral Wrapped outer conductors for superior shielding under flexure. These cables are used as flexible cable alternatives to semirigid cable and in many cases use the same connectors.

TWINAX**.....233**



Pasternack offers two versions of Twinax cable with an impedance of 100 or 78 ohms. Twinax cable has two center conductors surrounded by a dielectric. The dielectric is surrounded by a braided outer conductor covered by a PVC jacket material. This construction creates a shielded, twisted pair with superior performance when compared to unshielded, twisted pair cable.

COAXIAL CABLES

Meets or Exceeds MIL-C-17 Specifications Where Applicable

MODEL NO.	COAX IMPEDANCE (Ohm) / MAXIMUM FREQUENCY (GHz.)	JACKET DIAMETER (in) / CONDUCTOR DIAM.(in) [strands]	NUMBER OF SHIELDS / RF SHIELDING (min dB)	VELOCITY FACTOR (%) / ATTENUATION AT 1 GHz. (dB/100 ft)	MAX. POWER HANDLING AT 1 GHz (W) / MAXIMUM OPERATING VOLTAGE (V RMS)	JACKET MATERIAL / MINIMUM BEND RADIUS (in)	PRICE PER FOOT 1-99 FT / 500-999 FT	PRICE PER FOOT 100-499 FT / 1000 + FT	ROW
75 OHM BROADCAST									
LMR-400-75	75 2.5	0.405 0.065[1]	2 90	85		PE 1	$1.49 $1.49	$1.49 $1.49	1
PE-B150	75 5	0.150 0.017[7]	1	20	25 600	PVC	$1.39 $1.25	$1.32 $1.20	2
PE-B159-BK	75 3	0.159 0.023[1]	2	83 10.5	300	PVC 1.5	$1.35 $1.22	$1.28 $1.16	3
PE-B159-BL	75 3	0.159 0.023[1]	2	83 10.5	300	PVC 1.5	$1.43 $1.29	$1.36 $1.23	4
PE-B159-GR	75 3	0.159 0.023[1]	2	83 10.5	300	PVC 1.5	$1.17 $1.05	$1.11 $1.01	5
PE-B159-RD	75 3	0.159 0.023[1]	2	83 10.5	300	PVC 1.5	$1.23 $1.11	$1.17 $1.06	6
PE-B159-WH	75 3	0.159 0.023[1]	2	83 10.5	300	PVC 1.5	$1.09 $0.98	$1.04 $0.94	7
PE-B159-YW	75 3	0.159 0.023[1]	2	83 10.5	300	PVC 1.5	$1.15 $1.04	$1.09 $0.99	8
PE-B305	75 1	0.305 0.031[1]	2	9.2	52 2,900	PVC	$3.47 $3.12	$3.30 $2.98	9
RG11A/U	75 1	0.405 [7]	1 45	66 8.11	150	PVC	$3.03 $2.73	$2.88 $2.61	10
RG179B/U	75 3	0.100 0.012[7]	1	70 29.15	900	FEP	$3.93 $3.54	$3.73 $3.38	11
RG187A/U	75 3	0.102 0.012[7]	1	70 25	200 2,000	PTFE	$5.79 $5.21	$5.50 $4.98	12
RG302/U	75 3	0.206 0.025[7]	1	69 13	650 1,700	FEP	$9.38 $8.44	$8.91 $8.07	13
RG59B/U	75 1	0.242 0.022[1]	1	66 11.5	77 2,300	PVC (NC)	$1.49 $1.34	$1.42 $1.28	14
RG6A/U	75 1	0.332 0.029[1]	2 90	66 11	100	PVC (NC)	$7.39 $6.65	$7.02 $6.36	15
RG6-CATV	75 3	0.278 0.04[1]	3 70	85 6.55	6.5	PVC (NC)	$1.79 $1.61	$1.70 $1.54	16
COMMUNICATIONS									
LMR-200-UF	50 5.8	0.195 0.044	2 90	83 12.18		TPE 0.5	$2.57 $2.57	$2.57 $2.57	17
LMR-100A-FR	50 5.8	0.110 0.018[1]	2 90	66 24		FRPE 0.25	$0.79 $0.79	$0.79 $0.79	18
LMR-100A-PVC	50 5.8	0.110 0.018[1]	2 90	66 24		PVC 0.25	$0.82 $0.82	$0.82 $0.82	19
LMR-100A-UF	50 5.8	0.110 0.018[1]	2 90	66 24		TPE 0.25	$0.99 $0.99	$0.99 $0.99	20
LMR-195	50 5.8	0.195 0.037[1]	2 90	80 11.8		PE 0.5	$0.83 $0.83	$0.83 $0.83	21
LMR-195-FR	50 5.8	0.195 0.037[1]	2 90	76 11.8		FRPE 0.5	$1.29 $1.29	$1.29 $1.29	22
LMR-195-UF	50 5.8	0.195 0.038[1]	2 90	74 13.89		TPE 0.5	$1.13 $1.13	$1.13 $1.13	23
LMR-200	50 5.8	0.195 0.044[1]	2 90	83 10.5		PE 0.5	$0.87 $0.87	$0.87 $0.87	24
LMR-200-FR	50 5.8	0.195 0.044[1]	2 90	83		FRPE 0.5	$1.23 $1.23	$1.23 $1.23	25
LMR-240	50 5.8	0.240 0.056[1]	2 90	84 8		PE 0.75	$0.98 $0.98	$0.98 $0.98	26

See Our Website For Current Pricing & Real-Time Stock Availability!

COAXIAL CABLES

Meets or Exceeds MIL-C-17 Specifications Where Applicable

MODEL NO.	COAX IMPEDANCE (Ohm) / MAXIMUM FREQUENCY (GHz.)	JACKET DIAMETER (in) / CONDUCTOR DIAM.(in) [strands]	NUMBER OF SHIELDS / RF SHIELDING (min dB)	VELOCITY FACTOR (%) / ATTENUATION AT 1 GHz. (dB/100 ft)	MAX. POWER HANDLING AT 1 GHz (W) / MAXIMUM OPERATING VOLTAGE (V RMS)	JACKET MATERIAL / MINIMUM BEND RADIUS (in)	PRICE PER FOOT 1-99 FT 500-999 FT	PRICE PER FOOT 100-499 FT 1000 + FT	ROW
COMMUNICATIONS									
LMR-240-DB	50 5.8	0.240 0.056[1]	2 90	84 7.66		PE 0.75	$1.33 $1.33	$1.33 $1.33	27
LMR-240-FR	50 5.8	0.240 0.056[1]	2 90	83 7.99		FRPE 0.75	$1.57 $1.57	$1.57 $1.57	28
LMR-240-UF	50 5.8	0.240 0.056	2 90	84 9.19		TPE 0.75	$1.19 $1.19	$1.19 $1.19	29
LMR-400	50 6	0.405 0.108[1]	2 90	85 4.25		PE 1	$1.59 $1.59	$1.59 $1.59	30
LMR-400-DB	50 6	0.405 0.108[1]	2 90	85 4.15		PE 1	$1.48 $1.48	$1.48 $1.48	31
LMR-400-FR	50 5.8	0.405 0.108[1]	2 90	84 4.1		FRPE 1	$2.45 $2.45	$2.45 $2.45	32
LMR-400-UF	50 5.8	0.405 0.108	2 90	85 5		TPE 1	$2.03 $2.03	$2.03 $2.03	33
LMR-500	50 5.8	0.500 0.142[1]	2 90	86 3.1		PE 1.25	$2.17 $2.17	$2.17 $2.17	34
LMR-500-DB	50 5.8	0.500 0.142[1]	2 90	86 3.1		PE 1.25	$2.43 $2.43	$2.43 $2.43	35
LMR-500-UF	50 5.8	0.500 0.142[1]	2 90	85 4		TPE 1.25	$3.29 $3.29	$3.29 $3.29	36
LMR-600	50 5.8	0.590 0.176[1]	2 90	87 2.62		PE 1.5	$2.89 $2.89	$2.89 $2.89	37
LMR-600-DB	50 5.8	0.590 0.176[1]	2 90	87 2.62		PE 1.5	$2.98 $2.98	$2.98 $2.98	38
LMR-600-FR	50 5.8	0.590 0.176[1]	2 90	85 2.64		PE 1.5	$4.23 $4.23	$4.23 $4.23	39
LMR-600-UF	50 5.8	0.590 0.176[1]	2 90	87 3.17		TPE 1.5	$3.67 $3.67	$3.67 $3.67	40
LMR-LW195	50 8	0.195 0.037[1]	2 90	80 11.67		PE 0.5	$0.67 $0.67	$0.67 $0.67	41
LMR-LW240	50 8	0.240 0.056[1]	2 90	83 7.99		PE 0.75	$0.84 $0.84	$0.84 $0.84	42
LMR-LW400	50 8	0.405 0.108[1]	2 90	84 4.1		PE 1	$1.13 $1.13	$1.13 $1.13	43
LMR-LW600	50 8	0.590 0.176[1]	2 90	85 2.64		PE 1.5	$2.15 $2.15	$2.15 $2.15	44
PE-1/2FAC	50 8.8	0.629 0.189[1]	1 120	88 2.2		PE 2.75	$7.39 $6.65	$7.02 $6.36	45
PE-1/2SFHC	50 10.2	0.519 0.141[1]	1 120	82 3.41	1,000	PE 0.6	$6.69 $6.02	$6.36 $5.75	46
PE-1/4SFHC	50 20.4	0.303 0.074[1]	1 120	82 5.85		PE 0.5	$5.09 $4.58	$4.84 $4.38	47
PE-B400	50 4	0.403 0.103[1]	2	6	190 600	PVC	$2.93 $2.64	$2.78 $2.52	48
PE-C100-LSZH	50 5.8	0.109 0.018[1]	2 90	66 25	40	LSZH 0.25	$2.09 $1.88	$1.99 $1.80	49
PE-C195	50 5.8	0.195 0.037[1]	2 90	80 11.7	135	PE 0.5	$1.19 $1.07	$1.13 $1.02	50
PE-C200	50 5.8	0.195 0.044[1]	2 90	83 10.8	170 1,000	PE	$1.37 $1.23	$1.30 $1.18	51
PE-C240	50 5.8	0.240 0.056[1]	2 90	84 7.98	250	PE 0.75	$1.85 $1.67	$1.76 $1.59	52
PE-C300	50 2.5	0.300 0.07[1]	2	85 6.3	350 2,000	PE 1.5	$4.63 $4.17	$4.40 $3.98	53

See Our Website For Current Pricing & Real-Time Stock Availability!

COAXIAL CABLES

Meets or Exceeds MIL-C-17 Specifications Where Applicable

MODEL NO.	COAX IMPEDANCE (Ohm) / MAXIMUM FREQUENCY (GHz.)	JACKET DIAMETER (in) / CONDUCTOR DIAM.(in) [strands]	NUMBER OF SHIELDS / RF SHIELDING (min dB)	VELOCITY FACTOR (%) / ATTENUATION AT 1 GHz. (dB/100 ft)	MAX. POWER HANDLING AT 1 GHz (W) / MAXIMUM OPERATING VOLTAGE (V RMS)	JACKET MATERIAL / MINIMUM BEND RADIUS (in)	PRICE PER FOOT 1-99 FT / 500-999 FT	PRICE PER FOOT 100-499 FT / 1000 + FT	ROW
COMMUNICATIONS									
PE-C400	50 5.8	0.405 0.108[1]	2 90	85 4.1	480	PE	$2.07 $1.86	$1.97 $1.78	54
PE-C500	50 6	0.500 0.142[1]	2 90	86 3.5	720 3,000	PE	$7.09 $6.38	$6.74 $6.10	55
PE-C600	50 5.8	0.590 0.176[1]	2 90	87 2.7	900	PE	$3.73 $3.36	$3.54 $3.21	56
HIGH PERFORMANCE									
PE-P047	50 50	0.056 0.011[1]	2 90	70 35	43	FEP 0.2	$11.79 $10.61	$11.20 $10.14	57
PE-P086	50 18	0.104 0.02[1]	2 110	70 21.7		FEP	$11.19 $10.07	$10.63 $9.62	58
PE-P086HF	50 40	0.104 0.02[1]	2	70 21.1		FEP 0.52	$10.39 $9.35	$9.87 $8.94	59
PE-P141	50 18	0.163 0.037[1]	2 110	70 11.2	600	FEP	$16.99 $15.29	$16.14 $14.61	60
PE-P141HF	50 31	0.163 0.037[1]	2	70 13		FEP 0.82	$19.19 $17.27	$18.23 $16.50	61
PE-P142LL	50 18	0.195 0.051[1]	3	80 8.2	820	FEP	$18.79 $16.16	$17.47 $15.03	62
PE-P160LL	50 18	0.160 0.04[1]	3	83 11	560	FEP	$26.39 $22.70	$24.54 $21.11	63
PE-P195	50 22	0.195 0.037[1]	3	70 12.5	650 1,900	FEP	$14.19 $12.77	$13.48 $12.20	64
PE-P300LL	50 18	0.300 0.089[1]	3	83 5.1	1,700	FEP	$33.59 $28.89	$31.24 $26.87	65
RG MIL-C-17 TYPE CABLE									
RG141A/U	50 10	0.190 0.037[1]	1	70 13	650	PTFE (FG)	$9.38 $8.44	$8.91 $8.07	66
RG142B/U	50 8	0.195 0.037[1]	2	70 12.9	1,900	FEP	$8.39 $7.55	$7.97 $7.22	67
RG174A/U	50 1	0.110 0.019[7]	1	66 32	17	PVC	$0.84 $0.76	$0.80 $0.72	68
RG178B/U	50 3	0.072 0.012[7]	1	70 44.41	55 1,000	FEP	$1.53 $1.38	$1.45 $1.32	69
RG180B/U	95 3	0.141 0.012[7]	1	70	250	FEP	$6.29 $5.66	$5.98 $5.41	70
RG188A/U	50 3	0.110 0.02[7]	1	26	160	PTFE	$3.93 $3.54	$3.73 $3.38	71
RG188-DS	50 10	0.118 0.02[7]	2	30	160	PTFE	$5.28 $4.75	$5.02 $4.54	72
RG196A/U	50 1	0.080 0.011[7]	1	49	78	PTFE	$1.95 $1.76	$1.85 $1.68	73
RG213/U	50 1	0.405 0.09[7]	1	66 9	190 3,700	PVC	$2.73 $2.46	$2.59 $2.35	74
RG214/U	50 11	0.425 0.089[7]	2	66 7.32	170 5,000	PVC	$11.79 $10.61	$11.20 $10.14	75
RG217/U	50 1	0.545 0.106[1]	2	66 5.8	260 5,200	PVC	$6.79 $6.11	$6.45 $5.84	76
RG218/U	50 1	0.870 0.195[1]	1	66 5	600 11,000	PVC	$16.99 $15.29	$16.14 $14.61	77
RG223/U	50 12.4	0.209 0.035[1]	2	66 13.41	50 1,900	PVC	$4.17 $3.75	$3.96 $3.59	78

See Our Website For Current Pricing & Real-Time Stock Availability!

COAXIAL CABLES

Meets or Exceeds MIL-C-17 Specifications Where Applicable

MODEL NO.	COAX IMPEDANCE (Ohm) / MAXIMUM FREQUENCY (GHz.)	JACKET DIAMETER (in) / CONDUCTOR DIAM.(in) [strands]	NUMBER OF SHIELDS / RF SHIELDING (min dB)	VELOCITY FACTOR (%) / ATTENUATION AT 1 GHz. (dB/100 ft)	MAX. POWER HANDLING AT 1 GHz (W) / MAXIMUM OPERATING VOLTAGE (V RMS)	JACKET MATERIAL / MINIMUM BEND RADIUS (in)	PRICE PER FOOT 1-99 FT / 500-999 FT	PRICE PER FOOT 100-499 FT / 1000 + FT	ROW
RG MIL-C-17 TYPE CABLE									
RG225/U	50 10	0.430 0.094[7]	2	70 7.5	1,700 3,700	PTFE (FG)	$45.79 $41.21	$43.50 $39.38	79
RG303/U	50 3	0.170 0.037[1]	1	 14	650	FEP	$8.79 $7.91	$8.35 $7.56	80
RG316/U	50 3	0.102 0.02[7]	1	69 38	 900	FEP	$3.85 $3.47	$3.66 $3.31	81
RG316-DS	50 3	0.114 0.02[7]	2 85	70 29	120 1,200	FEP 0.59	$4.59 $4.13	$4.36 $3.95	82
RG393/U	50 10	0.390 0.094[7]	2	70 7.5	1,700	FEP	$22.39 $20.15	$21.27 $19.26	83
RG400/U	50 12.4	0.195 [19]	2	70 14.7	600 1,900	FEP	$10.59 $9.53	$10.06 $9.11	84
RG55B/U	53 3	0.202 0.032[1]	2	66 16.5	53	PE	$3.79 $3.41	$3.60 $3.26	85
RG58C/U	50 5	0.195 0.036[19]	1	66 20	44 1,900	PVC (NC) 0.98	$1.19 $1.07	$1.13 $1.02	86
RG58-P (1)	53 1	0.159 0.032[1]	1 45	70 17.3	143	FEP	$11.39 $10.25	$10.82 $9.80	87
RG62A/U	93 1	0.239 0.025[1]	1 45	83 8.7	77	PVC	$3.45 $3.11	$3.28 $2.97	88
RG8A/U	50 1	0.405 0.085[7]	1	66 8	190	PVC (NC)	$4.87 $4.38	$4.63 $4.19	89
RG8X	50 1	0.242 0.056[19]	1	 13.5	60 2,500	PVC (NC)	$5.39 $4.85	$5.12 $4.64	90
SEMIRIGID AND FORMABLE									
PECX001	50 115	 0.013[1]	1	77 30	101	 0.125	$16.79 $15.11	$15.95 $14.44	91
PECX002	50 115	 0.013[1]	1	77 30	101	 0.125	$20.19 $18.17	$19.18 $17.36	92
PECX003	50 72	 0.02[1]	1	77 20	188	 0.25	$23.59 $21.23	$22.41 $20.29	93
PECX004	50 72	 0.02[1]	1	77 20	188	 0.25	$26.59 $23.93	$25.26 $22.87	94
PECX005	50 62	 0.023[1]	1	77 17	314	 0.25	$11.19 $10.07	$10.63 $9.62	95
PECX006	50 62	 0.023[1]	1	77 17	231	 0.25	$13.99 $12.59	$13.29 $12.03	96
PECX007	50 34	 0.04[1]	1	77 10.5	580	 0.5	$18.59 $16.73	$17.66 $15.99	97
PECX008	50 34	 0.04[1]	1	77 10.5	580	 0.5	$18.59 $16.73	$17.66 $15.99	98
TFT-402	50 5.8	0.160 0.037[1]	2 -80	76		FEP 0.75	$4.37 $4.37	$4.37 $4.37	99
PE-020SR (8)	50 27	 0.004[1]	1	 85	2.9		$26.99 $24.29	$25.64 $23.21	1
PE-034SR (2,8)	50 40	 0.008[1]	1	 60	10		$14.59 $13.13	$13.86 $12.55	2
PE-047SR (3,8)	50 40	 0.011[1]	1	 40	32		$13.99 $12.59	$13.29 $12.03	3
PE-047SR-STRAIGHT	50 40	0.047 0.011[1]	1	 40		 0.05	$14.99 $13.49	$14.24 $12.89	4
PE-118SR (2)	50 46	 0.032[1]	1	 12.5	500 3,000	 0.4	$53.99 $48.59	$51.29 $46.43	5

See Our Website For Current Pricing & Real-Time Stock Availability!

COAXIAL CABLES

Meets or Exceeds MIL-C-17 Specifications Where Applicable

MODEL NO.	COAX IMPEDANCE (Ohm) / MAXIMUM FREQUENCY (GHz.)	JACKET DIAMETER (in) / CONDUCTOR DIAM.(in) [strands]	NUMBER OF SHIELDS / RF SHIELDING (min dB)	VELOCITY FACTOR (%) / ATTENUATION AT 1 GHz. (dB/100 ft)	MAX. POWER HANDLING AT 1 GHz (W) / MAXIMUM OPERATING VOLTAGE (V RMS)	JACKET MATERIAL / MINIMUM BEND RADIUS (in)	PRICE PER FOOT 1-99 FT / 500-999 FT	PRICE PER FOOT 100-499 FT / 1000 + FT	ROW
SEMIRIGID AND FORMABLE									
PE-SR047AL (3,6)	50 20	 0.011[1]	1 90	70 41	32		$12.79 $11.51	$12.15 $11.00	6
PE-SR047AL-STRAIGHT	50 20	0.047 0.011[1]	1 90	70 41	1,000	0.05	$13.99 $12.59	$13.29 $12.03	7
PE-SR047FL (12)	50 20	 0.011[1]	1	70 36	32		$12.19 $10.97	$11.58 $10.48	8
PE-SR401AL-STRAIGHT	50 18	 0.064	1	70 7.5	661		$28.19 $25.37	$26.78 $24.24	9
PE-SR401FL (11)	50 18	 0.065[1]	1 100	70 6.8	279	 0.75	$23.99 $21.59	$22.79 $20.63	10
PE-SR402-75 (3,8)	75 36	 0.02[1]	1	 12.5	280 3,500	 0.1	$13.59 $12.23	$12.91 $11.69	11
PE-SR402-75-STRAIGHT	75 36	 0.02[1]	1	 12.5			$13.99 $12.59	$13.29 $12.03	12
PE-SR402AL (3,10)	50 36	 0.036[1]	1	70 13	450		$12.79 $11.51	$12.15 $11.00	13
PE-SR402AL-STRAIGHT	50 36	0.141 0.036[1]	1	70 13		0.1	$13.19 $11.87	$12.53 $11.34	14
PE-SR402FL (4)	50 20	 0.037[1]	 110	70 12	400		$10.59 $9.53	$10.06 $9.11	15
PE-SR402FLJ (13)	50 34	0.161 0.036[1]	 100	70 11.89	303.4 1,900	FEP 0.315	$13.39 $12.05	$12.72 $11.52	16
PE-SR402TN	50 36	 0.036		70 12		 1	$7.99 $7.19	$7.59 $6.87	17
PE-SR402TN-STRAIGHT	50 36	 0.036		70 12		 1	$10.99 $9.89	$10.44 $9.45	18
PE-SR405AL (3,9)	50 40	 0.02[1]	1	 23	130	 0.05	$12.19 $10.97	$11.58 $10.48	19
PE-SR405AL-STRAIGHT	50 40	 0.02[1]	1	 23		 0.05	$11.99 $10.79	$11.39 $10.31	20
PE-SR405FL (5)	50 20	 0.02[1]	1	70 22.5	105		$15.99 $14.39	$15.19 $13.75	21
PE-SR405FLJ (14)	50 61	0.105 0.02[1]	1 100	70 19.5	121.5 1,500	FEP 0.5	$12.39 $11.15	$11.77 $10.66	22
PE-SR405TN	50 40	 0.02[1]	1	 22		 0.05	$7.78 $7.00	$7.39 $6.69	23
PE-SR405TN-STRAIGHT	50 40	 0.02[1]	1	 22		 0.05	$9.19 $8.27	$8.73 $7.90	24
RG401/U (2,8)	50 20	 0.064[1]	1	70 7.5	1,400 3,000		$29.99 $26.99	$28.49 $25.79	25
RG402/U (3,8)	50 34	 0.036[1]	1	70 11.1	450		$8.99 $8.09	$8.54 $7.73	26
RG402/U-STRAIGHT	50 33	 0.036[1]	1	70 12	450		$10.59 $9.53	$10.06 $9.11	27
RG405/U (3,8)	50 40	 0.02[1]	1 -110	70 22	130		$10.19 $9.17	$9.68 $8.76	28
RG405/U-STRAIGHT	50 40	 0.02[1]	1 -110	70 22	130		$12.59 $11.33	$11.96 $10.83	29
SPF-250	50 5.8	0.303 0.075[1]	1	83		FRPE 1.25	$3.35 $3.35	$3.35 $3.35	30
SPF-375	50 6	0.435 0.11[1]	1	83		FRPE 1.75	$4.07 $4.07	$4.07 $4.07	31
SPF-500	50 6	0.545 0.14[1]	1	83		FRPE 2.25	$4.59 $4.59	$4.59 $4.59	32

See Our Website For Current Pricing & Real-Time Stock Availability!

COAXIAL CABLES

Meets or Exceeds MIL-C-17 Specifications Where Applicable

MODEL NO.	COAX IMPEDANCE (Ohm) / MAXIMUM FREQUENCY (GHz.)	JACKET DIAMETER (in) / CONDUCTOR DIAM.(in) [strands]	NUMBER OF SHIELDS / RF SHIELDING (min dB)	VELOCITY FACTOR (%) / ATTENUATION AT 1 GHz. (dB/100 ft)	MAX. POWER HANDLING AT 1 GHz (W) / MAXIMUM OPERATING VOLTAGE (V RMS)	JACKET MATERIAL / MINIMUM BEND RADIUS (in)	PRICE PER FOOT 1-99 FT / 500-999 FT	PRICE PER FOOT 100-499 FT / 1000 + FT	ROW
SEMIRIGID AND FORMABLE									
SPO-250	50 5.8	0.303 0.075[1]	1	83		PE 1.25	$2.89 $2.89	$2.89 $2.89	33
SPO-375	50 6	0.430 0.11[1]	1	83		PE 1.75	$3.18 $3.18	$3.18 $3.18	34
SPO-500	50 6	0.530 0.14[1]	1	83		PE 2.25	$3.27 $3.27	$3.27 $3.27	35
SPP-250-LLPL	50 5.8	0.280 0.068[1]	1 100	76 5.5	650	FEP 1.25	$6.39 $6.39	$6.39 $6.39	36
SPP-375-LLPL	50 5.8	0.402 0.108[1]	1 100	76		FEP 1.25	$8.49 $8.49	$8.49 $8.49	37
SPP-500-LLPL	50 5.8	0.500 0.136[1]	1	76		FEP 1.5	$11.19 $11.19	$11.19 $11.19	38
TFT-402-LF	50 5.8	0.160 0.037[1]	2 80	76		FEP 0.75	Call Call	Call Call	39
TWINAX									
PE-S330 (TWINAX)	100 0.4	0.330 0.037[7]	2		300	PVC	$7.09 $6.38	$6.74 $6.10	40
RG108A/U (TWINAX)	78 1	0.235 0.038[7]	1	66 34.6	30	PVC	$3.97 $3.57	$3.77 $3.41	41

NOTES:

(1) P = PLENUM CABLE, NEC 725-2(b) CLASS 2 - REQUIRES SPECIAL CONNECTORS
(2) SEMI-RIGID CABLE, SOLD IN 5 FEET, STRAIGHT PIECES ONLY
(3) SEMI-RIGID CABLE, SOLD IN EITHER 5 FEET, STRAIGHT PIECES OR COILS OF 50 FEET
(4) RE-SHAPEABLE VERSION OF RG402/U
(5) RE-SHAPEABLE VERSION OF RG405/U
(6) TINNED ALUMINUM VERSION OF PE-047SR
(7) TINNED ALUMINUM VERSION OF RG401/U
(8) BARE COPPER JACKET
(9) TINNED ALUMINUM VERSION OF RG405/U
(10) TINNED ALUMINUM VERSION OF RG402/U
(11) RE-SHAPEABLE VERSION OF RG401/U
(12) RE-SHAPEABLE VERSION OF PE-047SR
(13) JACKETED RE-SHAPEABLE VERSION OF RG402/U
(14) JACKETED RE-SHAPEABLE VERSION OF RG405/U

MATERIALS:

Al (Tn)	TIN PLATED ALUMINUM
Cu	BARE COPPER
Cu (Tn)	TIN PLATED COPPER
FEP	FLUORINATED ETHYLENE PROPYLENE
LSZH	LOW SMOKE ZERO HALOGEN
PE	POLYETHYLENE
PTFE	POLYTETRAFLUOROETHYLENE
PTFE (FR)	FIBERGLASS REINFORCED PTFE
PVC	POLYVINYLCHLORIDE
PVC (NC)	NON-CONTAMINATED PVC
PVC (FR)	FIBERGLASS REINFORCED PVC

See Our Website For Current Pricing & Real-Time Stock Availability!

Connector Selection Guide

3 Easy Ways to Find your Product.....

1. Search by PE Part Number

If you know the PE part number you are searching for, please reference our Part Number Index on Page 404

2. Quick Reference Guide

(Page number refers to first appearance of product in the Connector Section)

Connector Series	Page
1.0/2.3	240
1.0mm	240
1.85mm	240
2.2-5	242
2.4mm	243
2.92mm	244
3.5mm	245
4.1/9.5 Mini DIN	246
4.3-10	246
7/16 DIN	247
10-32	241
75 Ohm 1.0/2.3	294
75 Ohm 1.6/5.6	294
75 Ohm BNC	295
75 Ohm F	297
75 Ohm HD-BNC	298
75 Ohm MCX	298

Connector Series	Page
75 Ohm Mini SMB	299
75 Ohm N	299
75 Ohm RCA	300
75 Ohm SMB	300
75 Ohm SMB Positive Snap	301
75 Ohm SMC	301
75 Ohm TNC	302
BNC Twinax	303
3/4"-20 Twinax	303
Banana	304
BMA	249
BNC	251
C	255
Double Banana	304
D-Sub	256
FAKRA	256

Connector Series	Page
FME	257
GR874	258
HN	258
LC	258
MC-Card	259
MCX	259
MHV	260
Mini SMP	261
Mini UHF	262
MMBX	262
MMCX	263
N	264
NEX10	269
NMO Mount	269
QMA	270
QN	270
Rev. Pol. BNC	253

Connector Series	Page
Rev. Pol. MCX	263
Rev. Pol. N	269
Rev. Pol. SMA	278
Rev. Pol. TNC	291
Rev. Thread SMA	280
SC	271
SHV	271
SMA	272
SMB	281
SMC	282
SMP	283
SSMA	285
SSMB	287
SSMC	287
TNC	289
UHF	293
UMCX	294

3. Connector Locator

Connector Type	Page
1.0/2.3 Jack Connectors	
Right angle, Bulkhead, Cable Connectors	240
Right angle, PCB Mount	240
Straight, Bulkhead, Cable Connectors	240
Straight, Bulkhead, PCB Mount	240
Straight, PCB Mount	240
1.0/2.3 Plug Connectors	
Right angle, Cable Connectors	240
Straight, Cable Connectors	240
1.0mm Female Connectors	
Straight, PCB Mount	240
1.85mm Female Connectors	
Straight, 2 Hole Flange, Field Replaceable Contact	241
Straight, 4 Hole Flange, Field Replaceable Contact	241
Straight, Bulkhead, Cable Connectors	241
Straight, Cable Connectors	241
Straight, PCB Mount	241
1.85mm Male Connectors	
Straight, Cable Connectors	240
Straight, PCB Mount	241
Straight, Threaded, Field Replaceable Contact	241
2.2-5 Female Connectors	
Straight, Bulkhead, Cable Connectors	242
Straight, Cable Connectors	242

Connector Type	Page
2.2-5 Male Connectors	
Right angle, Cable Connectors	242
Straight, Cable Connectors	242
2.4mm Female Connectors	
Straight, 2 Hole Flange, Field Replaceable Contact	243
Straight, 4 Hole Flange, Field Replaceable Contact	244
Straight, Bulkhead, Field Replaceable Contact	243
Straight, Field Replaceable Contact	243
2.4mm Male Connectors	
Straight, 2 Hole Flange, Field Replaceable Contact	243
Straight, Field Replaceable Contact	243
2.92mm Female Connectors	
Straight, 2 Hole Flange, Field Replaceable Contact	245
Straight, 4 Hole Flange, Cable Connectors	245
Straight, 4 Hole Flange, Field Replaceable Contact	245
Straight, Bulkhead, Cable Connectors	245
Straight, Cable Connectors	244
Straight, PCB Mount	244
2.92mm Male Connectors	
Straight, 2 Hole Flange, Field Replaceable Contact	244
Straight, Cable Connectors	244
Straight, PCB Mount	244
3.5mm Female Connectors	
Straight, Bulkhead, Cable Connectors	246

Connector Locator

Connector Type	Page
Straight, Cable Connectors	246
3.5mm Male Connectors	
Straight, Cable Connectors	245
4.1/9.5 Mini DIN Female Connectors	
Straight, Bulkhead, Cable Connectors	246
Straight, Cable Connectors	246
4.1/9.5 Mini DIN Male Connectors	
Right angle, Cable Connectors	246
Straight, Cable Connectors	246
4.3-10 Female Connectors	
Straight, 4 Hole Flange, Cable Connectors	247
Straight, 4 Hole Flange, Terminal	247
Straight, Bulkhead, Cable Connectors	247
Straight, Cable Connectors	247
4.3-10 Male Connectors	
Right angle, Cable Connectors	247
Straight, Cable Connectors	246
7/16 DIN Female Connectors	
Straight, 4 Hole Flange, Cable Connectors	249
Straight, 4 Hole Flange, Terminal	249
Straight, Bulkhead, Cable Connectors	249
Straight, Bulkhead, Terminal	249
Straight, Cable Connectors	248
7/16 DIN Male Connectors	
Right angle, Cable Connectors	248
Straight, Cable Connectors	247
10-32 Female Connectors	
Right angle, PCB Mount	242
Straight, Bulkhead, Cable Connectors	242
Straight, Bulkhead, Terminal	242
Straight, Cable Connectors	242
Straight, PCB Mount	242
10-32 Male Connectors	
Right angle, Cable Connectors	242
Straight, Cable Connectors	241
75 Ohm 1.0/2.3 Female Connectors	
Right angle, Bulkhead, PCB Mount	294
Straight, PCB Mount	294
75 Ohm 1.0/2.3 Jack Connectors	
Right angle, Bulkhead, PCB Mount	294
Straight, Bulkhead, PCB Mount	294
75 Ohm 1.0/2.3 Male Connectors	
Straight, Cable Connectors	294
75 Ohm 1.0/2.3 Plug Connectors	
Straight, Cable Connectors	294
75 Ohm 1.6/5.6 Jack Connectors	
Right angle, Bulkhead, Cable Connectors	295
Right angle, PCB Mount	295
Straight, Bulkhead, PCB Mount	295
75 Ohm 1.6/5.6 Plug Connectors	
Right angle, Cable Connectors	295
Straight, Cable Connectors	294
75 Ohm BNC Female Connectors	
Right angle, 4 Hole Flange, Terminal	296
Right angle, Bulkhead, PCB Mount	296
Right angle, Bulkhead, Terminal	296
Straight, 4 Hole Flange, Cable Connectors	296
Straight, 4 Hole Flange, Terminal	296
Straight, Bulkhead, Cable Connectors	296
Straight, Bulkhead, PCB Mount	296
Straight, Bulkhead, Terminal	296
Straight, Cable Connectors	296
Straight, PCB Mount	296
75 Ohm BNC Male Connectors	
Right angle, Cable Connectors	296
Straight, 4 Hole Flange, Terminal	295
Straight, Bulkhead, Terminal	295
Straight, Cable Connectors	295
75 Ohm F Female Connectors	
Right angle, Bulkhead, PCB Mount	298
Right angle, PCB Mount	297
Straight, 4 Hole Flange, Terminal	297
Straight, Bulkhead, Cable Connectors	297
Straight, Bulkhead, PCB Mount	297
Straight, Bulkhead, Terminal	297
Straight, PCB Mount	297
Straight, Thread-In, Terminal	297
75 Ohm F Male Connectors	
Right angle, Cable Connectors	297
Straight, Cable Connectors	297
75 Ohm HD-BNC Female Connectors	
Right angle, Bulkhead, PCB Mount	298
Straight, Bulkhead, PCB Mount	298
Straight, PCB Mount	298
75 Ohm HD-BNC Male Connectors	
Straight, Cable Connectors	298
75 Ohm MCX Jack Connectors	
Right angle, PCB Mount	298
Straight, Cable Connectors	298
Straight, PCB Mount	298
75 Ohm MCX Plug Connectors	
Right angle, Cable Connectors	298
Straight, Cable Connectors	298
75 Ohm Mini SMB Jack Connectors	
Right angle, Bulkhead, PCB Mount	299
Right angle, PCB Mount	299
Straight, 2 Hole Flange, Terminal	299
Straight, PCB Mount	299
75 Ohm Mini SMB Plug Connectors	
Right angle, Cable Connectors	299
Straight, Cable Connectors	299
75 Ohm N Female Connectors	
Straight, 4 Hole Flange, Terminal	300
Straight, Bulkhead, Terminal	300
Straight, Cable Connectors	299
75 Ohm N Male Connectors	
Right angle, Cable Connectors	299
Straight, 4 Hole Flange, Terminal	299

Connector Locator

Connector Type	Page
Straight, Cable Connectors	299
75 Ohm RCA Female Connectors	
Straight, Bulkhead, Cable Connectors	300
75 Ohm RCA Male Connectors	
Right angle, Cable Connectors	300
Straight, Cable Connectors	300
75 Ohm SMB Jack Connectors	
Right angle, PCB Mount	301
Straight, Bulkhead, Cable Connectors	301
Straight, Bulkhead, Terminal	301
Straight, Cable Connectors	301
Straight, PCB Mount	301
75 Ohm SMB Plug Connectors	
Right angle, Cable Connectors	300
Straight, Bulkhead, Terminal	300
Straight, Cable Connectors	300
Straight, PCB Mount	300
75 Ohm SMB Positive Snap Plug Connectors	
Right angle, Cable Connectors	301
Straight, Cable Connectors	301
75 Ohm SMC Jack Connectors	
Right angle, PCB Mount	302
Straight, Bulkhead, Cable Connectors	302
Straight, Bulkhead, Terminal	302
Straight, Cable Connectors	302
Straight, PCB Mount	302
75 Ohm SMC Plug Connectors	
Right angle, Cable Connectors	301
Right angle, PCB Mount	302
Straight, Bulkhead, Terminal	301
Straight, Cable Connectors	301
75 Ohm TNC Female Connectors	
Straight, 4 Hole Flange, Terminal	302
Straight, Bulkhead, Cable Connectors	302
Straight, Bulkhead, Terminal	302
75 Ohm TNC Male Connectors	
Right angle, Cable Connectors	302
Straight, Cable Connectors	302
78 Ohm BNC Twinax Jack Connectors	
Right angle, PCB Mount	303
Straight, 4 Hole Flange, Terminal	303
Straight, Bulkhead, Cable Connectors	303
Straight, Bulkhead, Terminal	303
Straight, Cable Connectors	303
Straight, PCB Mount	303
78 Ohm BNC Twinax Plug Connectors	
Straight, Cable Connectors	303
95 Ohm 3/4”-20 Twinax Female Connectors	
Straight, 4 Hole Flange, Terminal	303
Straight, Bulkhead, Terminal	303
Straight, Cable Connectors	303
95 Ohm 3/4”-20 Twinax Male Connectors	
Straight, Cable Connectors	303
Banana Plug Connectors	
Straight, Cable Connectors	304
BMA Jack Connectors	
Right angle, 2 Hole Flange, Cable Connectors	251
Straight, 2 Hole Flange, Cable Connectors	250
Straight, 2 Hole Flange, Terminal	250
Straight, 4 Hole Flange, Terminal	250
Straight, Bulkhead, Cable Connectors	250
Straight, Cable Connectors	250
Straight, PCB Mount	250
Straight, Terminal	250
Straight, Thread-In, Terminal	250
BMA Plug Connectors	
Right angle, PCB Mount	250
Straight, 2 Hole Flange, Field Replaceable Contact	249
Straight, 2 Hole Flange, Terminal	249
Straight, 4 Hole Flange, Terminal	250
Straight, Bulkhead, Cable Connectors	249
Straight, PCB Mount	249
Straight, Thread-In, Terminal	250
BNC Female Connectors	
Right angle, 4 Hole Flange, Terminal	253
Right angle, Bulkhead, Terminal	253
Right angle, PCB Mount	253
Straight, 4 Hole Flange, Cable Connectors	253
Straight, 4 Hole Flange, Terminal	253
Straight, Bulkhead, Cable Connectors	252
Straight, Bulkhead, PCB Mount	253
Straight, Bulkhead, Terminal	253
Straight, Cable Connectors	252
Straight, PCB Mount	252
BNC Male Connectors	
Right angle, Cable Connectors	252
Straight, 4 Hole Flange, Terminal	251
Straight, Bulkhead, Terminal	251
Straight, Cable Connectors	251
C Female Connectors	
Straight, 4 Hole Flange, Cable Connectors	255
Straight, 4 Hole Flange, Terminal	255
Straight, Bulkhead, Cable Connectors	255
Straight, Bulkhead, Terminal	255
Straight, Cable Connectors	255
C Male Connectors	
Right angle, Cable Connectors	255
Straight, 4 Hole Flange, Terminal	255
Straight, Cable Connectors	255
Double Banana Plug Connectors	
Straight, Cable Connectors	304
D-Sub Plug Connectors	
Right angle, Cable Connectors	256
Straight, Cable Connectors	256
D-Sub Receptacle Connectors	
Right angle, Cable Connectors	256
Straight, Cable Connectors	256
FAKRA Jack Connectors	

Connector Locator

Connector Type	Page
Right angle, Cable Connectors	257
Right angle, PCB Mount	257
Straight, Cable Connectors	257
FAKRA Plug Connectors	
Right angle, PCB Mount	256
Straight, Cable Connectors	256
Straight, PCB Mount	256
FME Jack Connectors	
Straight, Cable Connectors	257
FME Plug Connectors	
Straight, Bulkhead, Terminal	257
Straight, Cable Connectors	257
GR874 Sexless Connectors	
Straight, Cable Connectors	258
HN Female Connectors	
Straight, 4 Hole Flange, Terminal	258
Straight, Bulkhead, Terminal	258
Straight, Cable Connectors	258
HN Male Connectors	
Right angle, Cable Connectors	258
Straight, Cable Connectors	258
LC Female Connectors	
Straight, 4 Hole Flange, Terminal	259
Straight, Cable Connectors	259
LC Male Connectors	
Right angle, Cable Connectors	258
Straight, Cable Connectors	258
MC-Card Plug Connectors	
Right angle, Cable Connectors	259
Straight, Cable Connectors	259
MCX Jack Connectors	
Right angle, Bulkhead, Terminal	260
Right angle, PCB Mount	260
Straight, 2 Hole Flange, Terminal	260
Straight, Bulkhead, Cable Connectors	260
Straight, Bulkhead, Terminal	260
Straight, Cable Connectors	260
Straight, PCB Mount	260
MCX Plug Connectors	
Right angle, Cable Connectors	259
Right angle, PCB Mount	259
Straight, Cable Connectors	259
Straight, PCB Mount	259
MHV Female Connectors	
Straight, 4 Hole Flange, Cable Connectors	261
Straight, 4 Hole Flange, Terminal	261
Straight, Bulkhead, Cable Connectors	261
Straight, Bulkhead, Terminal	261
Straight, Cable Connectors	260
MHV Male Connectors	
Right angle, Cable Connectors	260
Straight, Cable Connectors	260
Mini SMP Female Connectors	
Right angle, Cable Connectors	261
Straight, Cable Connectors	261

Connector Type	Page
Mini SMP Male Connectors	
Right angle, PCB Mount	261
Straight, PCB Mount	261
Straight, Solder, Terminal	261
Mini UHF Female Connectors	
Straight, 4 Hole Flange, Terminal	262
Straight, Bulkhead, Cable Connectors	262
Straight, Bulkhead, PCB Mount	262
Straight, Bulkhead, Terminal	262
Straight, Cable Connectors	262
Mini UHF Male Connectors	
Straight, Cable Connectors	262
MMBX Jack Connectors	
Straight, PCB Mount	262
Straight, Thread-In, Terminal	262
MMBX Plug Connectors	
Right angle, Cable Connectors	262
Straight, Cable Connectors	262
Straight, PCB Mount	262
MMCX Jack Connectors	
Right angle, PCB Mount	263
Straight, Cable Connectors	263
Straight, PCB Mount	263
MMCX Plug Connectors	
Right angle, Cable Connectors	263
Straight, Cable Connectors	263
Straight, PCB Mount	263
N Female Connectors	
Right angle, 4 Hole Flange, Terminal	268
Right angle, Bulkhead, PCB Mount	268
Straight, 2 Hole Flange, Terminal	268
Straight, 4 Hole Flange, Cable Connectors	268
Straight, 4 Hole Flange, Terminal	268
Straight, Bulkhead, Cable Connectors	267
Straight, Bulkhead, PCB Mount	268
Straight, Bulkhead, Terminal	268
Straight, Cable Connectors	266
Straight, PCB Mount	267
Straight, Press-In, Terminal	268
N Male Connectors	
Right angle, Cable Connectors	265
Straight, 4 Hole Flange, Terminal	265
Straight, Bulkhead, Terminal	265
Straight, Cable Connectors	264
NEX10 Female Connectors	
Straight, Bulkhead, Cable Connectors	269
Straight, Cable Connectors	269
NEX10 Male Connectors	
Right angle, Cable Connectors	269
Straight, Cable Connectors	269
NMO Mount Sexless Connectors	
Straight, Cable Connectors	269
QMA Female Connectors	
Right angle, PCB Mount	270
Straight, Bulkhead, Cable Connectors	270

Connector Locator

Connector Type	Page
Straight, Cable Connectors	270
Straight, PCB Mount	270
QMA Male Connectors	
Right angle, Cable Connectors	270
Straight, Cable Connectors	270
QN Female Connectors	
Straight, 4 Hole Flange, Terminal	271
Straight, Bulkhead, Cable Connectors	271
QN Male Connectors	
Right angle, Cable Connectors	271
Straight, Cable Connectors	270
Reverse Polarity BNC Female Connectors	
Right angle, Bulkhead, Terminal	254
Straight, 4 Hole Flange, Terminal	254
Straight, Bulkhead, Cable Connectors	254
Straight, Bulkhead, Terminal	254
Straight, Cable Connectors	254
Reverse Polarity BNC Male Connectors	
Right angle, Cable Connectors	254
Straight, 4 Hole Flange, Terminal	254
Straight, Cable Connectors	253
Reverse Polarity MCX Jack Connectors	
Right angle, Bulkhead, PCB Mount	264
Straight, Bulkhead, Cable Connectors	263
Straight, Bulkhead, PCB Mount	263
Reverse Polarity MCX Plug Connectors	
Right angle, Cable Connectors	263
Straight, Cable Connectors	263
Reverse Polarity N Female Connectors	
Straight, Cable Connectors	269
Reverse Polarity N Male Connectors	
Straight, Cable Connectors	269
Reverse Polarity SMA Female Connectors	
Right angle, Bulkhead, PCB Mount	280
Right angle, PCB Mount	279
Straight, 2 Hole Flange, Terminal	279
Straight, 4 Hole Flange, Terminal	279
Straight, Bulkhead, Cable Connectors	279
Straight, Bulkhead, PCB Mount	279
Straight, Bulkhead, Terminal	279
Straight, Cable Connectors	278
Straight, PCB Mount	279
Reverse Polarity SMA Male Connectors	
Right angle, Cable Connectors	278
Straight, Cable Connectors	278
Reverse Polarity TNC Female Connectors	
Straight, 4 Hole Flange, Terminal	293
Straight, Bulkhead, Cable Connectors	292
Straight, Bulkhead, Terminal	293
Straight, Cable Connectors	292
Reverse Polarity TNC Male Connectors	
Right angle, Cable Connectors	292
Straight, 4 Hole Flange, Terminal	292
Straight, Cable Connectors	291

Connector Type	Page
Reverse Thread SMA Female Connectors	
Right angle, PCB Mount	280
Straight, 4 Hole Flange, Terminal	280
Straight, Bulkhead, Cable Connectors	280
Straight, Cable Connectors	280
Straight, PCB Mount	280
Reverse Thread SMA Male Connectors	
Right angle, Cable Connectors	280
Straight, Cable Connectors	280
SC Female Connectors	
Straight, Bulkhead, Terminal	271
SC Male Connectors	
Right angle, Cable Connectors	271
Straight, Cable Connectors	271
SHV Jack Connectors	
Straight, 4 Hole Flange, Terminal	272
Straight, Bulkhead, Cable Connectors	272
Straight, Bulkhead, Terminal	272
SHV Plug Connectors	
Straight, Bulkhead, Terminal	271
Straight, Cable Connectors	271
SMA Female Connectors	
Right angle, 2 Hole Flange, Terminal	278
Right angle, 4 Hole Flange, Field Replaceable Contact	278
Right angle, 4 Hole Flange, Terminal	278
Right angle, Bulkhead, PCB Mount	278
Right angle, Bulkhead, Terminal	278
Right angle, PCB Mount	277
Straight, 2 Hole Flange, Cable Connectors	276
Straight, 2 Hole Flange, Field Replaceable Contact	276
Straight, 2 Hole Flange, Terminal	277
Straight, 4 Hole Flange, Cable Connectors	277
Straight, 4 Hole Flange, Field Replaceable Contact	277
Straight, 4 Hole Flange, Terminal	277
Straight, Bulkhead, Cable Connectors	275
Straight, Bulkhead, PCB Mount	276
Straight, Bulkhead, Terminal	276
Straight, Cable Connectors	274
Straight, PCB Mount	275
Straight, Press-In, Terminal	277
SMA Male Connectors	
Right angle, Cable Connectors	274
Straight, 2 Hole Flange, Field Replaceable Contact	273
Straight, 2 Hole Flange, Terminal	273
Straight, 4 Hole Flange, Field Replaceable Contact	273
Straight, 4 Hole Flange, Terminal	274
Straight, Bulkhead, Terminal	273
Straight, Cable Connectors	272
Straight, PCB Mount	273
SMB Jack Connectors	
Right angle, Bulkhead, PCB Mount	282
Right angle, Bulkhead, Terminal	282
Right angle, PCB Mount	282
Straight, 2 Hole Flange, Terminal	282

Connector Locator

Connector Type	Page
Straight, 4 Hole Flange, Terminal	282
Straight, Bulkhead, Cable Connectors	281
Straight, Bulkhead, PCB Mount	282
Straight, Bulkhead, Terminal	282
Straight, Cable Connectors	281
Straight, PCB Mount	281
SMB Plug Connectors	
Right angle, Cable Connectors	281
Right angle, PCB Mount	281
Straight, Bulkhead, Terminal	281
Straight, Cable Connectors	281
Straight, PCB Mount	281
SMC Jack Connectors	
Right angle, Bulkhead, Terminal	283
Right angle, PCB Mount	283
Straight, 4 Hole Flange, Terminal	283
Straight, Bulkhead, Cable Connectors	283
Straight, Bulkhead, PCB Mount	283
Straight, Bulkhead, Terminal	283
Straight, Cable Connectors	283
Straight, PCB Mount	283
SMC Plug Connectors	
Right angle, Cable Connectors	282
Right angle, PCB Mount	283
Straight, Cable Connectors	282
Straight, PCB Mount	282
SMP Female Connectors	
Right angle, Cable Connectors	285
Straight, Cable Connectors	285
Straight, PCB Mount	285
SMP Male Connectors	
Right angle, PCB Mount	285
Straight, 2 Hole Flange, Cable Connectors	284
Straight, 2 Hole Flange, Shroud	284
Straight, 2 Hole Flange, Terminal	284
Straight, Bulkhead, Cable Connectors	284
Straight, PCB Mount	283
Straight, Shroud	284
Straight, Terminal	284
Straight, Thread-In, Shroud	285
Straight, Thread-In, Terminal	285
SSMA Female Connectors	
Right angle, PCB Mount	287
Straight, 2 Hole Flange, Cable Connectors	286
Straight, 2 Hole Flange, Terminal	286
Straight, 4 Hole Flange, Cable Connectors	286
Straight, 4 Hole Flange, Terminal	287
Straight, Bulkhead, Cable Connectors	286
Straight, Bulkhead, PCB Mount	286
Straight, Bulkhead, Terminal	286
Straight, Cable Connectors	286
Straight, PCB Mount	286
SSMA Male Connectors	
Right angle, Cable Connectors	286
Straight, 4 Hole Flange, Terminal	286
Straight, Cable Connectors	285
Straight, PCB Mount	286
SSMB Jack Connectors	
Right angle, PCB Mount	287
Straight, 4 Hole Flange, Terminal	287
Straight, Bulkhead, Cable Connectors	287
Straight, Bulkhead, Terminal	287
Straight, Cable Connectors	287
Straight, PCB Mount	287
SSMB Plug Connectors	
Right angle, Cable Connectors	287
Straight, Cable Connectors	287
SSMC Jack Connectors	
Right angle, Bulkhead, Cable Connectors	288
Right angle, Bulkhead, PCB Mount	288
Right angle, Bulkhead, Terminal	288
Right angle, PCB Mount	288
Straight, 2 Hole Flange, Terminal	288
Straight, 4 Hole Flange, Terminal	288
Straight, Bulkhead, Cable Connectors	288
Straight, Bulkhead, Terminal	288
Straight, PCB Mount	288
SSMC Plug Connectors	
Right angle, Cable Connectors	288
Right angle, PCB Mount	288
Straight, Cable Connectors	287
TNC Female Connectors	
Right angle, Bulkhead, Cable Connectors	291
Right angle, Bulkhead, PCB Mount	291
Right angle, Bulkhead, Terminal	291
Right angle, PCB Mount	291
Straight, 4 Hole Flange, Cable Connectors	291
Straight, 4 Hole Flange, Terminal	291
Straight, Bulkhead, Cable Connectors	290
Straight, Bulkhead, PCB Mount	291
Straight, Bulkhead, Terminal	291
Straight, Cable Connectors	290
TNC Male Connectors	
Right angle, Cable Connectors	289
Straight, 4 Hole Flange, Terminal	289
Straight, Cable Connectors	289
TNC Sexless Connectors	
Straight, Cable Connectors	290
UHF Female Connectors	
Straight, 4 Hole Flange, Terminal	294
Straight, Bulkhead, Terminal	293
Straight, Cable Connectors	293
UHF Male Connectors	
Straight, Cable Connectors	293
UHF Sexless Connectors	
Straight, Cable Connectors	293
UMCX Jack Connectors	
Straight, PCB Mount	294

1.0/2.3 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE44244	$19.39	$18.42	$17.45	$16.68	1
			RG188-DS, RG316-DS	PE45166	$15.39	$14.62	$13.85	$13.24	2
			RG55, RG142, RG223, RG400	PE44242	$17.39	$16.52	$15.65	$14.96	3
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE44243	$19.99	$18.99	$17.99	$17.19	4
		Solder/Solder	TFT-402, TFT-402-LF	TC-402-1023M-LP	$17.79	$17.79	$17.79	$17.79	5
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE44249	$19.39	$18.42	$17.45	$16.68	6
			RG316-DS, RG188-DS	PE44783	$21.39	$20.32	$19.25	$18.40	7
			RG55, RG142, RG223, RG400	PE44247	$20.39	$19.37	$18.35	$17.54	8
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE44248	$22.39	$21.27	$20.15	$19.26	9
	Jack								
PCB Mount		Solder	Thru Hole with .200 inch x .055 inch Hole Spacing	PE44257	$13.39	$12.72	$12.05	$11.52	10
	Jack, Bulkhead Mount								
Cable Connectors		Crimp/Solder	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100A-FR, PE-C100, PE-B100 with .217 inch DD Hole	PE44254	$22.19	$21.08	$19.97	$19.08	11
		Solder/Solder	PE-SR405AL, PE-SR405FL, RG405 with .235 inch D Hole	PE44256	$24.59	$23.36	$22.13	$21.15	12
PCB Mount		Solder	Thru Hole with .220 inch Diameter	PE44259	$16.59	$15.76	$14.93	$14.27	13
	Jack Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .055 inch Hole Spacing	PE44258	$16.99	$16.14	$15.29	$14.61	14
	Jack Right Angle, Bulkhead Mount								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188 with .236 inch DD Hole	PE44261	$20.79	$19.75	$18.71	$17.88	15
			RG58 with .236 inch DD Hole	PE44260	$21.19	$20.13	$19.07	$18.22	16

1.0mm Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	See Web for Volume Pricing	ROW
	Female						
PCB Mount		Clamp	Vertical Launch	PE45692	$403.99	See Web for Volume Pricing	17
		Clamp/Solder (Captive Contact)	End Launch	PE45403	$1,330.00		18

1.85mm Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	See Web for Volume Pricing	ROW
	Male						
Cable Connectors		Clamp/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44799	$155.99		19
			PE-P086, PE-P086LL	PE45005	$113.99		20

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

1.85mm Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	PRICE See Web for Volume Pricing	ROW
	Male						
Cable Connectors		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE45410	$115.99	See Web for Volume Pricing	21
			PECX001, PECX002	PE45482	$143.99		22
			PECX003, PECX004	PE45484	$143.99		23
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44336	$193.99		24
			PE-SR405AL, RG405, PE-SR405FLJ	PE45413	$121.99		25
PCB Mount		Clamp	Vertical Launch	PE45690	$103.99		26
			Vertical Launch	PE45691	$103.99		27
		Clamp/Solder (Captive Contact)	End Launch	PE45517	$355.99		28
			End Launch	PE45518	$335.99		29
	Male, Threaded Mount						
Field Replaceable		Field Replaceable	.009 inch Pin	PE44338	$191.99		30
	Female						
Cable Connectors		Clamp/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44800	$175.99	See Web for Volume Pricing	31
PCB Mount		Clamp	Vertical Launch	PE45688	$94.99		32
			Vertical Launch	PE45689	$94.99		33
		Clamp/Solder (Captive Contact)	End Launch	PE45402	$291.99		34
			End Launch	PE45477	$213.99		35
			End Launch	PE45515	$313.99		36
			End Launch	PE45516	$311.99		37
	Female, Bulkhead Mount						
Cable Connectors		Clamp/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405 with .252 inch D Hole	PE44802	$165.99		38
	Female, 2 Hole Flange Mount						
Field Replaceable		Field Replaceable	0.009 inch Pin	PE45632	$93.99	See Web for Volume Pricing	39
			0.009 inch Pin	PE45633	$85.99		40
			with EMI gasket, accepts 0.23mm (.009inch) pin	PE45716	$101.99		41
			with EMI gasket, accepts 0.23mm (.009inch) pin	PE45750	$101.99		42
			with EMI gasket, accepts 0.3mm (.012inch) pin	PE45731	$101.99		43
			with EMI gasket, accepts 0.3mm (.012inch) pin	PE45749	$101.99		44
			with EMI gasket, accepts 0.3mm (.012inch) pin	PE45751	$101.99		45
			with EMI gasket, accepts 0.51mm (.020inch) pin	PE45748	$101.99		46
	Female, 4 Hole Flange Mount						
Field Replaceable		Field Replaceable	0.009 inch Pin	PE45631	$72.99		47
			0.009 inch Pin with .340 inch Hole Spacing	PE45630	$75.99		48
			with EMI gasket, accepts 0.23mm (.009inch) pin	PE45714	$101.99		49
			with EMI gasket, accepts 0.23mm (.009inch) pin	PE45715	$101.99		50
			with EMI gasket, accepts 0.3mm (.012inch) pin	PE45729	$101.99		51
			with EMI gasket, accepts 0.3mm (.012inch) pin	PE45730	$101.99		52

10-32 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	PRICE 25-49	PRICE 50-99	PRICE 100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE44353	$45.19	$42.93	$40.67	$38.86	53
			RG178, RG196	PE44354	$53.99	$51.83	$50.21	$49.13	54
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE44351	$32.39	$30.77	$29.15	$27.86	55
			RG178, RG196	PE44352	$48.99	$46.54	$44.09	$42.13	56
			RG188-DS, RG316-DS	PE45170	$31.59	$30.01	$28.43	$27.17	57

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

10-32 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male Right Angle								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE44355	$32.59	$30.96	$29.33	$28.03	58
			RG178, RG196	PE44356	$53.99	$51.29	$48.59	$46.43	59
			RG316-DS, RG188-DS	PE45032	$32.99	$31.34	$29.69	$28.37	60
	Female								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE44363	$53.99	$51.29	$48.59	$46.43	61
			RG178, RG196	PE44364	$45.59	$43.31	$41.03	$39.21	62
		Crimp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE44361	$48.19	$45.78	$43.37	$41.44	63
			RG178, RG196	PE44362	$41.39	$39.73	$38.49	$37.66	64
			RG188-DS, RG316-DS	PE45171	$32.79	$31.15	$29.51	$28.20	65
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE44359	$31.59	$30.01	$28.43	$27.17	66
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100A-FR, PE-C100, PE-B100 with .295 inch D Hole	PE44367	$41.19	$39.13	$37.07	$35.42	67
			RG178, RG196 with .295 inch D Hole	PE44368	$47.39	$45.02	$42.65	$40.76	68
		Crimp/Solder	RG174, RG316, RG188 with .295 inch D Hole	PE44365	$44.39	$42.17	$39.95	$38.18	69
			RG178, RG196 with .295 inch D Hole	PE44366	$42.79	$40.65	$38.51	$36.80	70
Terminal		Solder	Solder Cup with .177 inch D Hole	PE44357	$34.19	$32.48	$30.77	$29.40	71
			Solder Cup with .295 inch D Hole	PE44358	$44.79	$42.55	$40.31	$38.52	72
	Female Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE44360	$38.59	$36.66	$34.73	$33.19	73

2.2-5 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45673	$21.39	$20.32	$19.25	$18.40	74
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45677	$28.39	$26.97	$25.55	$24.42	75
			TFT-402, TFT-402-LF	TC-402-225M-LP	$28.19	$28.19	$28.19	$28.19	76
	Male Right Angle								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45674	$29.79	$28.30	$26.81	$25.62	77
	Female								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45675	$21.39	$20.32	$19.25	$18.40	78
			TFT-402, TFT-402-LF	TC-402-225F-LP	$28.19	$28.19	$28.19	$28.19	79
	Female, Bulkhead Mount								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45676	$24.59	$23.36	$22.13	$21.15	80

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

2.4mm Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Field Replaceable		Clamp	Vertical Launch	PE45456	$58.99	$56.04	$53.09	$50.73	81
			Vertical Launch	PE45457	$60.99	$57.94	$54.89	$52.45	82
		Clamp/Solder (Captive Contact)	End Launch	PE45513	$261.99	$248.89	$235.79	$225.31	83
			End Launch	PE45514	$211.99	$201.39	$190.79	$182.31	84
		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE45411	$111.99	$106.39	$100.79	$96.31	85
			PE-SR405AL, PE-SR405FL, RG405	PE44215	$117.99	$112.09	$106.19	$101.47	86
			PE-SR405AL, RG405, PE-SR405FLJ	PE45414	$111.99	$106.39	$100.79	$96.31	87

2.4mm Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	See Web for Volume Pricing			ROW
	Male, 2 Hole Flange Mount								
Field Replaceable		Solder	Pin with .481 inch Hole Spacing	PE44220	$201.99				88
	Female								
Field Replaceable		Clamp	Vertical Launch	PE45454	$56.99		See Web for Volume Pricing		89
			Vertical Launch	PE45455	$56.99				90
		Clamp/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44216	$241.99				91
		Clamp/Solder (Captive Contact)	End Launch	PE45401	$217.99				92
			End Launch	PE45472	$119.99				93
			End Launch	PE45473	$113.99				94
			End Launch	PE45474	$111.99				95
			End Launch	PE45475	$111.99				96
			End Launch	PE45476	$119.99				97
			End Launch	PE45511	$235.99				98
			End Launch	PE45512	$261.99				99
	Female, Bulkhead Mount								
Field Replaceable		Clamp/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405 with .252 inch D Hole	PE44801	$177.99				1
	Female, 2 Hole Flange Mount								
Field Replaceable		Field Replaceable	0.009 inch Pin	PE45622	$70.99		See Web for Volume Pricing		2
			0.009 inch Pin	PE45626	$75.99				3
			0.009 inch Pin with .481 inch Hole Spacing	PE45618	$58.99				4
			0.012 inch Pin	PE45623	$56.99				5
			0.012 inch Pin	PE45627	$61.99				6
			0.012 inch Pin with .481 inch Hole Spacing	PE45619	$61.99				7
			0.015 inch Pin	PE45624	$59.99				8
			0.015 inch Pin	PE45628	$63.99				9
			0.015 inch Pin with .481 inch Hole Spacing	PE45620	$59.99				10
			0.02 inch Pin	PE45625	$62.99				11
			0.02 inch Pin	PE45629	$66.99				12
			0.02 inch Pin with .481 inch Hole Spacing	PE45621	$62.99				13
			with EMI gasket, accepts 0.23mm (.009inch) pin	PE45712	$66.99				14
			with EMI gasket, accepts 0.23mm (.009inch) pin	PE45740	$66.99				15
			with EMI gasket, accepts 0.23mm (.009inch) pin	PE45744	$66.99				16
			with EMI gasket, accepts 0.38mm (.015inch) pin	PE45713	$66.99				17
			with EMI gasket, accepts 0.38mm (.015inch) pin	PE45742	$66.99				18
			with EMI gasket, accepts 0.38mm (.015inch) pin	PE45746	$66.99				19
			with EMI gasket, accepts 0.3mm (.012inch) pin	PE45727	$66.99				20
			with EMI gasket, accepts 0.3mm (.012inch) pin	PE45741	$66.99				21
			with EMI gasket, accepts 0.3mm (.012inch) pin	PE45745	$66.99				22
			with EMI gasket, accepts 0.51mm (.020inch) pin	PE45728	$66.99				23
			with EMI gasket, accepts 0.51mm (.020inch) pin	PE45743	$66.99				24
			with EMI gasket, accepts 0.51mm (.020inch) pin	PE45747	$66.99				25

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

2.4mm Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, 4 Hole Flange Mount								
Field Replaceable		Field Replaceable	0.009 inch Pin	PE45614	$61.99	$58.89	$55.79	$53.31	26
			0.009 inch Pin with .340 inch Hole Spacing	PE45610	$68.99	$65.54	$62.09	$59.33	27
			0.012 inch Pin	PE45615	$49.19	$46.73	$44.27	$42.30	28
			0.012 inch Pin with .340 inch Hole Spacing	PE45611	$63.99	$60.79	$57.59	$55.03	29
			0.015 inch Pin	PE45616	$51.99	$49.39	$46.79	$44.71	30
			0.015 inch Pin with .340 inch Hole Spacing	PE45612	$56.99	$54.14	$51.29	$49.01	31
			0.02 inch Pin	PE45617	$54.99	$52.24	$49.49	$47.29	32
			0.02 inch Pin with .340 inch Hole Spacing	PE45613	$52.99	$50.34	$47.69	$45.57	33
			with EMI gasket, accepts 0.23mm (.009inch) pin	PE45708	$66.99	$63.64	$60.29	$57.61	34
			with EMI gasket, accepts 0.23mm (.009inch) pin	PE45710	$66.99	$63.64	$60.29	$57.61	35
			with EMI gasket, accepts 0.38mm (.015inch) pin	PE45709	$66.99	$63.64	$60.29	$57.61	36
			with EMI gasket, accepts 0.38mm (.015inch) pin	PE45711	$66.99	$63.64	$60.29	$57.61	37
			with EMI gasket, accepts 0.3mm (.012inch) pin	PE45723	$66.99	$63.64	$60.29	$57.61	38
			with EMI gasket, accepts 0.3mm (.012inch) pin	PE45725	$66.99	$63.64	$60.29	$57.61	39
			with EMI gasket, accepts 0.51mm (.020inch) pin	PE45724	$66.99	$63.64	$60.29	$57.61	40
			with EMI gasket, accepts 0.51mm (.020inch) pin	PE45726	$66.99	$63.64	$60.29	$57.61	41

2.92mm Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	See Web for Volume Pricing	ROW
	Male						
Cable Connectors		Clamp/Solder	PE-SR047FL, PE-SR047AL, PE-047SR	PE44797	$141.99	See Web for Volume Pricing	42
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44796	$103.99		43
		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE45412	$101.99		44
			PE-118SR, 0.118 inch	PE45486	$141.99		45
			PE-120SRLL, Tinned 120LL	PE45487	$133.99		46
			PECX001, PECX002	PE45483	$133.99		47
			PECX005, PECX006	PE45485	$135.99		48
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE4987	$60.99		49
			PE-SR405AL, PE-SR405FL, RG405	PE4988	$63.99		50
			PE-SR405AL, RG405, PE-SR405FLJ	PE45415	$101.99		51
PCB Mount		Clamp	Vertical Launch	PE45452	$55.99		52
			Vertical Launch	PE45453	$55.99		53
		Clamp/Solder (Captive Contact)	End Launch	PE45509	$227.99		54
			End Launch	PE45510	$215.99		55
	Male, 2 Hole Flange Mount						
Field Replaceable		Field Replaceable	.012 inch Pin with .481 inch Hole Spacing	PE44232	$86.99		56
	Female						
Cable Connectors		Clamp/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44798	$159.99	See Web for Volume Pricing	57
			PE-SR402AL, PE-SR402FL, RG402	PE44227	$161.99		58
PCB Mount		Clamp	Vertical Launch	PE45450	$52.99		59
			Vertical Launch	PE45451	$52.99		60
		Clamp/Solder (Captive Contact)	End Launch	PE45400	$205.99		61
			End Launch	PE45467	$87.99		62
			End Launch	PE45468	$87.99		63
			End Launch	PE45469	$87.99		64
			End Launch	PE45470	$87.99		65
			End Launch	PE45471	$82.99		66
			End Launch	PE45507	$207.99		67
			End Launch	PE45508	$195.99		68

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

2.92mm Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	PRICE See Web for Volume Pricing	ROW
	Female, Bulkhead Mount						
Cable Connectors		Clamp/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405 with .235 inch D Hole	PE4992	$205.99		69
	Female, 2 Hole Flange Mount						
Field Replaceable		Field Replaceable	.012 inch Pin with .481 inch Hole Spacing	PE44229	$149.99	See Web for Volume Pricing	70
			0.009 inch Pin	PE45602	$51.99		71
			0.009 inch Pin	PE45606	$51.99		72
			0.009 inch Pin with .481 inch Hole Spacing	PE45598	$58.99		73
			0.012 inch Pin	PE45603	$39.79		74
			0.012 inch Pin	PE45607	$41.99		75
			0.012 inch Pin with .481 inch Hole Spacing	PE45599	$47.39		76
			0.015 inch Pin	PE45604	$43.39		77
			0.015 inch Pin	PE45608	$43.39		78
			0.015 inch Pin with .481 inch Hole Spacing	PE45600	$43.39		79
			0.02 inch Pin	PE45605	$45.39		80
			0.02 inch Pin	PE45609	$45.39		81
			0.02 inch Pin with .481 inch Hole Spacing	PE45601	$43.99		82
			with EMI gasket, accepts 0.23mm (.009inch) pin	PE45706	$57.99		83
			with EMI gasket, accepts 0.23mm (.009inch) pin	PE45732	$57.99		84
			with EMI gasket, accepts 0.23mm (.009inch) pin	PE45736	$57.99		85
			with EMI gasket, accepts 0.23mm (.009inch) pin	PE45739	$57.99		86
			with EMI gasket, accepts 0.38mm (.015inch) pin	PE45707	$57.99		87
			with EMI gasket, accepts 0.38mm (.015inch) pin	PE45734	$57.99		88
			with EMI gasket, accepts 0.38mm (.015inch) pin	PE45738	$57.99		89
			with EMI gasket, accepts 0.3mm (.012inch) pin	PE45721	$57.99		90
			with EMI gasket, accepts 0.3mm (.012inch) pin	PE45733	$57.99		91
			with EMI gasket, accepts 0.3mm (.012inch) pin	PE45737	$57.99		92
			with EMI gasket, accepts 0.51mm (.020inch) pin	PE45722	$57.99		93
			with EMI gasket, accepts 0.51mm (.020inch) pin	PE45735	$57.99		94
	Female, 4 Hole Flange Mount						
Cable Connectors		Clamp/ Non-Solder Contact	PE-047SR, PE-SR047FL, PE-SR047AL	PE44905	$149.99	See Web for Volume Pricing	95
		Solder/ Non-Solder Contact	RG405, PE-SR405FL	PE44904	$147.99		96
Field Replaceable		Field Replaceable	0.009 inch Pin	PE45590	$52.99		97
			0.009 inch Pin with .340 inch Hole Spacing	PE45594	$55.99		98
			0.012 inch Pin	PE45591	$41.99		99
			0.012 inch Pin with .340 inch Hole Spacing	PE45595	$44.19		1
			0.015 inch Pin	PE45592	$44.19		2
			0.015 inch Pin with .340 inch Hole Spacing	PE45596	$45.39		3
			0.02 inch Pin	PE45593	$47.79		4
			0.02 inch Pin with .340 inch Hole Spacing	PE45597	$44.19		5
			with EMI gasket, accepts 0.23mm (.009inch) pin	PE45702	$57.99		6
			with EMI gasket, accepts 0.23mm (.009inch) pin	PE45704	$57.99		7
			with EMI gasket, accepts 0.38mm (.015inch) pin	PE45703	$57.99		8
			with EMI gasket, accepts 0.38mm (.015inch) pin	PE45705	$57.99		9
			with EMI gasket, accepts 0.3mm (.012inch) pin	PE45717	$57.99		10
			with EMI gasket, accepts 0.3mm (.012inch) pin	PE45719	$57.99		11
			with EMI gasket, accepts 0.51mm (.020inch) pin	PE45718	$57.99		12
			with EMI gasket, accepts 0.51mm (.020inch) pin	PE45720	$57.99		13

3.5mm Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	PRICE 25-49	PRICE 50-99	PRICE 100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE4981	$125.99	$119.69	$113.39	$108.35	14
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE4982	$127.99	$121.59	$115.19	$110.07	15

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

3.5mm Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	PRICE See Web for Volume Pricing			ROW
	Female								
Cable Connectors		Clamp/Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE45011	$127.99				16
		Threaded	VNA Test Cable	PE45398	$810.00				17
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	PE-SR402AL, PE-SR402FL, RG402 with .235 inch D Hole	PE4985	$349.99				18

4.1/9.5 Mini DIN Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45650	$18.79	$17.85	$16.91	$16.16	19
			SPP-250-LLPL	PE45421	$35.79	$34.00	$32.21	$30.78	20
			TFT-402, TFT-402-LF	TC-402-4195M-LP	$18.99	$18.99	$18.99	$18.99	21
	Male Right Angle								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45651	$24.59	$23.36	$22.13	$21.15	22
			SPP-250-LLPL	PE45422	$49.19	$46.73	$44.27	$42.30	23
			SPP-250-LLPL	TC-SPP250-4195M-RALP	$20.99	$20.99	$20.99	$20.99	24
	Female								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45652	$23.39	$22.22	$21.05	$20.12	25
			SPP-250-LLPL	PE45420	$40.19	$38.18	$36.17	$34.56	26
			TFT-402, TFT-402-LF	TC-402-4195F-LP	$14.79	$14.79	$14.79	$14.79	27
	Female, Bulkhead Mount								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45653	$26.59	$25.26	$23.93	$22.87	28

4.3-10 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	RG213, RG8, RG225, RG214, RG393	PE45295	$56.99	$54.14	$51.29	$49.01	29
			RG213, RG8, RG225, RG214, RG393	PE45296	$85.99	$81.69	$77.39	$73.95	30
		Crimp/ Non-Solder Contact	LMR-240	EZ-240-4310M-X	$23.39	$23.39	$23.39	$23.39	31
		Crimp/Solder	LMR-240	TC-240-4310M-X	$23.39	$23.39	$23.39	$23.39	32
			LMR-400	TC-400-4310M-X	$24.99	$24.99	$24.99	$24.99	33
			LMR-600	TC-600-4310M-X	$26.79	$26.79	$26.79	$26.79	34
		Solder/Solder	PE-1/2SFHC	PE45299	$25.99	$24.69	$23.39	$22.35	35
			PE-1/2SFHC	PE45300	$38.19	$36.28	$34.37	$32.84	36
			PE-1/4SFHC	PE45297	$53.99	$51.29	$48.59	$46.43	37
			PE-1/4SFHC	PE45298	$23.39	$22.22	$21.05	$20.12	38
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45654	$21.99	$20.89	$19.79	$18.91	39
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45658	$23.39	$22.22	$21.05	$20.12	40
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45659	$21.99	$20.89	$19.79	$18.91	41
			RG402, PE-SR402AL, PE-SR402FL, PE-SR402FLJ	PE45301	$39.79	$37.80	$35.81	$34.22	42

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

4.3-10 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Solder/Solder	SPO-375, SPF-375, SPP-375-LLPL	TC-375-4310M-LP	$23.39	$23.39	$23.39	$23.39	43
			SPP-250-LLPL	PE45418	$37.19	$35.33	$33.47	$31.98	44
			SPP-500-LLPL, SPO-500, SPF-500	TC-500-4310M-LP	$22.59	$22.59	$22.59	$22.59	45
			TFT-402, TFT-402-LF	TC-402-4310M-LP	$22.19	$22.19	$22.19	$22.19	46
			TFT-402, TFT-402-LF	TC-402-4310MS-LP	$23.39	$23.39	$23.39	$23.39	47
	Male Right Angle								
Cable Connectors		Solder/Solder	PE-1/2SFHC	PE45302	$60.99	$57.94	$54.89	$52.45	48
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45655	$25.19	$23.93	$22.67	$21.66	49
			RG402, PE-SR402AL, PE-SR402FL, PE-SR402FLJ	PE45303	$67.99	$64.59	$61.19	$58.47	50
			SPP-250-LLPL	PE45419	$49.19	$46.73	$44.27	$42.30	51
			SPP-250-LLPL, SPF-250, SPO-250, 1/4" Superflexible, PE-1/4SFHC	TC-250-4310M-RA-LP	$24.19	$24.19	$24.19	$24.19	52
			TFT-402, TFT-402-LF	TC-402-4310M-RA-LP	$23.39	$23.39	$23.39	$23.39	53
	Female								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45656	$23.39	$22.22	$21.05	$20.12	54
			SPP-250-LLPL	PE45417	$40.19	$38.18	$36.17	$34.56	55
			SPP-250-LLPL, SPO-250, SPF-250	TC-SPP250-4310F-LP	$19.59	$19.59	$19.59	$19.59	56
			TFT-402, TFT-402-LF	TC-402-4310F-LP	$22.59	$22.59	$22.59	$22.59	57
	Female, Bulkhead Mount								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45657	$24.59	$23.36	$22.13	$21.15	58
			TFT-402, TFT-402-LF	TC-402-4310F-BH-LP	$23.79	$23.79	$23.79	$23.79	59
	Female, 4 Hole Flange Mount								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45686	$25.99	$24.69	$23.39	$22.35	60
			RG402, PE-SR402AL, PE-SR402FL, PE-SR402FLJ	PE45304	$32.99	$31.34	$29.69	$28.37	61
Terminal		Solder	Solder Cup	PE45306	$25.39	$24.12	$22.85	$21.84	62

7/16 DIN Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	See Web for Volume Pricing	ROW
	Male						
Cable Connectors		Clamp/ Non-Solder Contact	1/2 inch Flexible, PE-1/2FAC	PE44738	$55.99	See Web for Volume Pricing	63
			1/2 inch Helical, 1/2 inch Superflexible, PE-1/2 Helical, PE-1/2SFHC	PE44732	$58.99		64
			1/4 inch Superflexible, PE-1/4SFHC	PE44728	$83.99		65
		Clamp/Solder	7/8 inch Annular	PE44568	$73.99		66
			7/8 inch Annular	PE44993	$60.99		67
			7/8 inch Helical	PE44558	$115.99		68
			PE-SR401AL, PE-SR401FL, RG401	PE44278	$57.99		69
			RG14, RG217	PE44276	$191.99		70
			RG17, RG218, RG219	PE44277	$209.99		71
			RG393, RG214, RG225, RG215, RG8	PE4567	$57.99		72
			RG58, RG55, RG141, RG142, RG223, RG400	PE45037	$143.99		73
		Crimp/ Non-Solder Contact	LMR-400, PE-C400, PE-B400, PE-B405	EZ-400-716M-X	$23.99		74
			LMR-600, PE-C600	EZ-600-716M-X	$27.79		75
			LMR-600, PE-C600	PE45001	$78.99		76
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44994	$56.99		77
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44538	$82.99		78
		Crimp/Solder	PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE44536	$51.99		79
			RG213, RG8	PE4570	$143.99		80
			RG214, RG9, RG225, RG393	PE4571	$74.99		81

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

7/16 DIN Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	PRICE See Web for Volume Pricing	ROW
	Male						
Cable Connectors		Crimp/Solder	RG55, RG141, RG142, RG223, RG400	PE4568	$111.99	See Web for Volume Pricing	82
			RG58	PE4569	$125.99		83
		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45660	$18.79		84
			SPP-250-LLPL	PE45424	$40.99		85
			SPP-250-LLPL, SPF-250, SPO-250, 1/4" Superflexible, PE-1/4SFHC	TC-250-716M-LP	$18.19		86
			SPP-375-LLPL, SPO-375, SPF-375	TC-375-716M-LP	$18.19		87
			SPP-500-LLPL, SPO-500, SPF-500	TC-500-716M-LP	$15.19		88
			TFT-402, TFT-402-LF	TC-402-716M-LP	$18.19		89
	Male Right Angle						
Cable Connectors		Clamp/ Non-Solder Contact	1/2 inch Annular, 1/2 inch Flexible, PE-1/2FAC	PE44569	$63.99	See Web for Volume Pricing	90
			1/2 inch Helical	PE44979	$53.99		91
		Clamp/Solder	RG14, RG217	PE44282	$277.99		92
			RG213, RG214, RG8, RG9, RG225, RG393, RG215	PE44280	$165.99		93
		Crimp/ Non-Solder Contact	LMR-400, PE-C400, PE-B400, PE-B405	EZ-400-716M-RA-X	$26.79		94
		Crimp/Solder	LMR-195, LMR-195-FR, PE-C195, PE-P195	PE45046	$55.99		95
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44541	$107.99		96
			PE-C600, .600 inch, LMR-600, LMR-600-DB	PE45640	$105.99		97
		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45661	$24.59		98
			SPP-250-LLPL	PE45425	$57.99		99
			SPP-250-LLPL	TC-SPP250-716M-RA-LP	$20.99		1
			TFT-402, TFT-402-LF	TC-402-716M-RA-LP	$23.39		2
	Female						
Cable Connectors		Clamp/ Non-Solder Contact	1/2 inch Flexible, PE-1/2FAC	PE44740	$45.99	See Web for Volume Pricing	3
			1/2 inch Superflexible, PE-1/2SFHC	PE44734	$58.99		4
		Clamp/Solder	1/2 inch Helical	PE44560	$52.99		5
			PE-SR401AL, PE-SR401FL, RG401	PE44289	$145.99		6
			PE-SR402AL, PE-SR402FL, RG402	PE44290	$137.99		7
			RG14, RG217	PE44288	$189.99		8
			RG213, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE44283	$193.99		9
			RG58, RG55, RG141, RG142, RG223, RG400	PE44285	$173.99		10
		Crimp/ Non-Solder Contact	PE-C240, LMR-240, RG8X	PE44545	$77.99		11
		Crimp/Solder	PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE44544	$48.19		12
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF	PE44546	$93.99		13
			RG213, RG8	PE44284	$159.99		14
			RG214, RG9, RG225, RG393	PE4575	$203.99		15
			RG55, RG142, RG223, RG400	PE44286	$177.99		16
			RG58	PE44287	$129.99		17
		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45662	$18.79		18
			SPP-250-LLPL	TC-SPP250-716F-LP	$15.79		19
			SPP-250-LLPL	PE45423	$40.19		20
			SPP-375-LLPL, SPO-375, SPF-375	TC-SPP375-716F-LP	$15.79		21
			TFT-402, TFT-402-LF	TC-402-716F-LP	$17.79		22

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

7/16 DIN Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	PRICE See Web for Volume Pricing	ROW
	Female, Bulkhead Mount						
Cable Connectors		Crimp/Solder	.195 inch, RG58, RG141, RG303, LMR-195, LMR-195-FR, PE-C195, PE-P195 with 1.161 inch DD Hole	PE44548	$129.99	See Web for Volume Pricing	23
			.400 inch, LMR-400, LMR-400-DB, LMR-400-UF, PE-B405, PE-C400, PE-B400 with 1.161 inch DD Hole	PE44550	$111.99		24
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44549	$97.99		25
			PE-C600, LMR-600, LMR-600-DB, .600 inch with 1.161 inch DD Hole	PE44551	$133.99		26
			RG55, RG142, RG223, RG400 with 1.161 inch DD Hole	PE44656	$95.99		27
		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45663	$32.79		28
Terminal		Solder	Solder Cup	PE4572	$213.99		29
	Female, 4 Hole Flange Mount						
Cable Connectors		Clamp/Solder	RG14, RG217 with .975 inch Hole Spacing	PE44292	$235.99		30
			RG214, RG213, RG393, RG8, RG225, RG215, RG9 with .975 inch Hole Spacing	PE44291	$227.99		31
		Solder/Solder	TFT-402, TFT-402-LF	TC-402-716F-PM-LP	$22.39		32
Terminal		Field Replaceable	Slotted Contact	PE44717	$169.99		33
		Solder	Solder Cup with .975 inch Hole Spacing	PE4573	$121.99		34
			Stub	PE45000	$69.99		35
		Threaded Pin	Pin with .975 inch Hole Spacing	PE4574	$111.99		36
			Pin with .975 inch Hole Spacing	PE4574A	$47.99		37

BMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	PRICE See Web for Volume Pricing	ROW
	Plug						
PCB Mount		Solder	Thru Hole	PE45335	$72.99		38
			Thru Hole	PE45336	$50.99		39
	Plug, Bulkhead Mount						
Cable Connectors		Crimp/Solder	RG142, RG223, RG400, RG55	PE45318	$43.79	See Web for Volume Pricing	40
			RG178, RG196	PE45315	$99.99		41
			RG188-DS, RG316-DS	PE45317	$44.99		42
			RG316, RG188, RG174, PE-C100, LMR-100A	PE45316	$61.99		43
		Solder/ Non-Solder Contact	RG402, PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN	PE45313	$73.99		44
			RG402, PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN	PE45314	$30.99		45
			RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN	PE45310	$55.99		46
			RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN	PE45311	$32.19		47
	Plug, 2 Hole Flange Mount						
Field Replaceable		Field Replaceable	.012 inch Pin with .481 inch Hole Spacing	PE45345	$273.99		48
			.020 inch Pin with .481 inch Hole Spacing	PE45346	$261.99		49
			.036 inch Pin with .481 inch Hole Spacing	PE45348	$86.99		50
Terminal		Solder	Stub with .481 inch Hole Spacing	PE45341	$49.59		51
			Stub with .481 inch Hole Spacing	PE45342	$44.79		52
			Stub with .481 inch Hole Spacing	PE45343	$14.99		53
			Stub with .481 inch Hole Spacing	PE45344	$25.39		54
			Stub with .481 inch Hole Spacing	PE45347	$81.99		55

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

BMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	PRICE See Web for Volume Pricing	ROW
	Plug, 4 Hole Flange Mount						
Terminal		Solder	Stub with .340 inch Hole Spacing	PE45339	$45.39		56
	Plug, Thread-In						
Terminal		None	Pin	PE45350	$145.99	See Web for Volume Pricing	57
			Pin	PE45351	$80.99		58
			Pin	PE45352	$149.99		59
			Pin	PE45353	$165.99		60
	Plug Right Angle						
PCB Mount		Solder	Surface Mount	PE45333	$165.99		61
			Thru Hole	PE45355	$47.59		62
	Jack						
Cable Connectors		Crimp/Solder	RG142, RG223, RG400, RG55	PE45320	$129.99		63
			RG316, RG188, RG174, PE-C100, LMR-100A	PE45319	$99.99		64
		Solder/ Non-Solder Contact	RG402, PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN	PE45328	$96.99		65
		Solder/Solder	RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ	PE45324	$88.99		66
			RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ	PE45325	$125.99		67
PCB Mount		Solder	Surface Mount	PE45338	$69.99		68
			Thru Hole	PE45337	$61.99		69
Terminal			Stub	PE45349	$227.99		70
	Jack, Bulkhead Mount						
Cable Connectors		Solder/Solder	RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ	PE45323	$57.99	See Web for Volume Pricing	71
	Jack, 2 Hole Flange Mount						
Cable Connectors		Crimp/Solder	RG316, RG188, RG174, LMR-100A, PE-C100-LSZH	PE45321	$67.99		72
		Solder/ Non-Solder Contact	RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ	PE45322	$67.99		73
		Solder/Solder	RG402, PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN	PE45326	$73.99		74
			RG402, PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN	PE45327	$46.79		75
Terminal		Solder	Stub	PE45340	$73.99		76
	Jack, 4 Hole Flange Mount						
Terminal		Solder	Stub with .340 inch Hole Spacing	PE45334	$72.99	See Web for Volume Pricing	77
	Jack, Thread-In						
Terminal		None	Pin	PE45354	$75.99		78

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

BMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Jack Right Angle, 2 Hole Flange Mount								
Cable Connectors		Crimp/Solder	RG142, RG223, RG400, RG55	PE45332	$71.99	$68.39	$64.79	$61.91	79
		Solder/Solder	RG402, PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN	PE45329	$86.99	$82.64	$78.29	$74.81	80
			RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ	PE45330	$94.99	$90.24	$85.49	$81.69	81
			RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ	PE45331	$79.99	$75.99	$71.99	$68.79	82

BNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	LMR-240, PE-C240	TC-240-BMC	$20.99	$20.99	$20.99	$20.99	83
			PE-B150, RG180, RG195	PE4383	$50.99	$48.44	$45.89	$43.85	84
			PE-B400, PE-B405, PE-C400, LMR-400, .400 inch	PE4386	$36.99	$35.14	$33.29	$31.81	85
			PE-C300	PE44042	$19.79	$18.80	$17.81	$17.02	86
			PE-SR401AL, PE-SR401FL, RG401	PE4380	$30.19	$28.68	$27.17	$25.96	87
			PE-SR402AL, PE-SR402FL, RG402	PE4206	$27.59	$26.21	$24.83	$23.73	88
			PE-SR405AL, PE-SR405FL, RG405	PE4207	$31.19	$29.63	$28.07	$26.82	89
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE4084	$20.59	$19.56	$18.53	$17.71	90
			RG178, RG196	PE4384	$22.39	$21.27	$20.15	$19.26	91
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4023	$12.79	$12.28	$11.89	$11.64	92
			RG59*, RG62*, RG71	PE4024	$13.99	$13.29	$12.59	$12.03	93
			RG6	PE4377	$22.99	$21.84	$20.69	$19.77	94
			RG8, RG215, RG225, RG214, RG393, RG213	PE4109	$25.79	$24.50	$23.21	$22.18	95
			RG8X, PE-C240, .240 inch, B7808A, LMR-240	PE4379	$24.99	$23.74	$22.49	$21.49	96
		Crimp/Crimp	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100, LMR-100-FR, PE-C100, PE-B100	PE45045	$11.39	$10.82	$10.25	$9.80	97
			RG316-DS, RG188-DS	PE45114	$11.19	$10.63	$10.07	$9.62	98
			RG59*, RG62*, RG71	PE4018	$12.99	$12.34	$11.69	$11.17	99
		Crimp/ Non-Solder Contact	LMR-400, PE-C400, LMR-400-DB	EZ-400-BM-X	$17.99	$17.99	$17.99	$17.99	1
		Crimp/Solder	LMR-200, PE-C200	TC-200-BM-X	$14.99	$14.99	$14.99	$14.99	2
			LMR-240, PE-C240	TC-240-BM-X	$12.59	$12.59	$12.59	$12.59	3
			LMR-400, PE-C400	TC-400-BM-X	$15.19	$15.19	$15.19	$15.19	4
			PE-B150, RG180, RG195	PE4247	$18.59	$17.66	$16.73	$15.99	5
			PE-B305	PE4210	$17.79	$16.90	$16.01	$15.30	6
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44640	$18.79	$17.85	$16.91	$16.16	7
			PE-C400, LMR-400	PE44294	$40.59	$38.56	$36.53	$34.91	8
			RG178, RG196	PE4643	$30.19	$28.68	$27.17	$25.96	9
			RG213, RG215, RG8	PE4378	$33.99	$32.29	$30.59	$29.23	10
			RG214, RG9, RG225, RG393	PE4351	$30.59	$29.06	$27.53	$26.31	11
			RG55, RG141, RG142, RG223, RG400	PE4044	$10.19	$9.68	$9.17	$8.76	12
			RG58 Plenum, RG122, RG58-P	PE4381	$34.19	$32.48	$30.77	$29.40	13
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4016	$9.19	$8.73	$8.27	$7.90	14
			RG59* Plenum, RG59*-P, RG302	PE4382	$24.59	$23.36	$22.13	$21.15	15
		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE4974	$50.99	$48.44	$45.89	$43.85	16
			PE-SR401AL, PE-SR401FL, RG401	PE4908	$64.99	$61.74	$58.49	$55.89	17
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE4650	$14.99	$14.24	$13.49	$12.89	18
			PE-SR405AL, PE-SR405FL, RG405	PE4651	$34.19	$32.48	$30.77	$29.40	19
	Male, Bulkhead Mount								
Terminal		Solder	Solder Cup with .350 inch D Hole	PE4211	$21.19	$20.13	$19.07	$18.22	20
	Male, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .531 inch Hole Spacing	PE4082	$23.19	$22.03	$20.87	$19.94	21

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

BNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE4307	$63.99	$60.79	$57.59	$55.03	22
			RG178, RG196	PE4388	$31.79	$30.20	$28.61	$27.34	23
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4387	$49.19	$46.73	$44.27	$42.30	24
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4053	$29.99	$28.49	$26.99	$25.79	25
		Crimp/Crimp	RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4298	$32.39	$30.77	$29.15	$27.86	26
		Crimp/Solder	PE-C200, LMR-200	PE44843	$26.19	$24.88	$23.57	$22.52	27
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44641	$33.79	$32.10	$30.41	$29.06	28
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE4393	$30.59	$29.06	$27.53	$26.31	29
			RG188-DS, RG316-DS	PE4396	$38.59	$36.66	$34.73	$33.19	30
			RG55, RG141, RG142, RG223, RG400	PE4345	$15.99	$15.19	$14.39	$13.75	31
			RG59*, RG62*, RG71	PE4195	$33.99	$32.29	$30.59	$29.23	32
		Solder/Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE4092	$49.39	$46.92	$44.45	$42.48	33
			PE-SR405AL, PE-SR405FL, RG405	PE45239	$51.99	$49.39	$46.79	$44.71	34
	Female								
Cable Connectors		Clamp/Solder	PE-SR401AL, PE-SR401FL, RG401	PE44674	$39.79	$37.80	$35.81	$34.22	35
			PE-SR402AL, PE-SR402FL, RG402	PE4204	$37.19	$35.33	$33.47	$31.98	36
			PE-SR405AL, PE-SR405FL, RG405	PE4205	$38.59	$36.66	$34.73	$33.19	37
			RG174, RG316, RG188	PE4321	$18.99	$18.04	$17.09	$16.33	38
			RG178, RG196	PE4389	$25.39	$24.12	$22.85	$21.84	39
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4212	$59.99	$56.99	$53.99	$51.59	40
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4058	$15.79	$15.00	$14.21	$13.58	41
			RG59*, RG62*, RG71	PE4057	$13.59	$12.91	$12.23	$11.69	42
		Crimp/Solder	PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE4070	$12.59	$11.96	$11.33	$10.83	43
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44642	$10.79	$10.25	$9.71	$9.28	44
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4079	$16.39	$15.57	$14.75	$14.10	45
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE45395	$18.79	$17.47	$16.16	$15.03	46
			RG55, RG141, RG142, RG223, RG400	PE4397	$14.79	$14.05	$13.31	$12.72	47
			RG59*, RG62*, RG71	PE4308	$12.19	$11.58	$10.97	$10.48	48
		Solder/Solder	PE-SR401FL, PE-SR401AL, RG401	PE45150	$40.19	$38.18	$36.17	$34.56	49
PCB Mount		Solder	End Launch	PE44616	$17.59	$16.71	$15.83	$15.13	50
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	PE-SR402AL, PE-SR402FL, RG402	PE4915	$44.99	$42.74	$40.49	$38.69	51
			PE-SR405AL, PE-SR405FL, RG405	PE4916	$41.59	$39.51	$37.43	$35.77	52
			RG174, RG316, RG188 with .480 inch D Hole	PE4319	$23.39	$22.22	$21.05	$20.12	53
			RG178, RG196 with .480 inch D Hole	PE4391	$27.99	$26.59	$25.19	$24.07	54
			RG214, RG213, RG393, RG8, RG225, RG11*, RG216*, RG144*, RG215, RG9 with .480 inch D Hole	PE4632	$64.99	$61.74	$58.49	$55.89	55
			RG316-DS, RG188-DS	PE44886	$39.99	$37.99	$35.99	$34.39	56
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, LMR-195, PE-C195, PE-P195 with .480 inch D Hole	PE4078	$28.39	$26.97	$25.55	$24.42	57
		Crimp/Crimp	RG58, PE-C195, PE-P195, LMR-195	PE45064	$20.19	$19.18	$18.17	$17.36	58
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch with .480 inch D Hole	PE4106	$21.79	$20.70	$19.61	$18.74	59
			RG178, RG196 with .480 inch D Hole	PE44658	$28.99	$27.54	$26.09	$24.93	60
			RG188-DS, RG316-DS with .480 inch D Hole	PE4392	$25.79	$24.50	$23.21	$22.18	61
			RG316, RG174, LMR-100	PE45131	$42.19	$40.08	$37.97	$36.28	62

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

BNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, Bulkhead Mount								
Cable Connectors		Crimp/Solder	RG55, RG142, RG223, RG400, RG141 with .480 inch D Hole	PE4209	$27.59	$26.21	$24.83	$23.73	63
			RG58 with .480 inch D Hole	PE4208	$18.59	$17.66	$16.73	$15.99	64
			RG59*, RG62*, RG71 with .480 inch D Hole	PE4309	$26.19	$24.88	$23.57	$22.52	65
PCB Mount		Solder	End Launch with .500 inch Diameter	PE44618	$25.99	$24.69	$23.39	$22.35	66
Terminal			Eyelet	PE44890	$35.19	$33.43	$31.67	$30.26	67
			Eyelet	PE44891	$117.99	$112.09	$106.19	$101.47	68
			Solder Cup with .350 inch D Hole	PE4015	$11.79	$11.20	$10.61	$10.14	69
			Solder Cup with .350 inch D Hole	PE4091	$12.59	$11.96	$11.33	$10.83	70
			Solder Cup with .410 inch D Hole	PE4014	$10.39	$9.87	$9.35	$8.94	71
			Solder Cup with .480 inch D Hole	PE4318	$25.79	$24.50	$23.21	$22.18	72
			Spade with .350 inch D Hole	PE4077	$29.39	$27.92	$26.45	$25.28	73
			Turret with .480 inch D Hole	PE4049	$24.59	$23.36	$22.13	$21.15	74
	Female, 4 Hole Flange Mount								
Cable Connectors		Clamp/Solder	RG316-DS, RG188-DS	PE44887	$50.99	$48.44	$45.89	$43.85	75
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, LMR-195, PE-C195, PE-P195 with .500 inch Threaded Hole Spacing	PE4056	$24.19	$22.98	$21.77	$20.80	76
		Solder/Solder	PE-047SR, PE-SR047FL, PE-SR047AL	PE44888	$52.99	$50.34	$47.69	$45.57	77
Terminal		Field Replaceable	Slotted Contact	PE44720	$67.99	$64.59	$61.19	$58.47	78
		Solder	Solder Cup with .500 inch Hole Spacing	PE4394	$18.39	$17.47	$16.55	$15.82	79
			Solder Cup with .500 inch Threaded Hole Spacing	PE4010	$12.99	$12.34	$11.69	$11.17	80
			Solder Cup with .718 inch Hole Spacing	PE4395	$30.71	$29.17	$27.64	$26.41	81
			Turret with .531 inch Hole Spacing	PE4011	$27.39	$26.02	$24.65	$23.56	82
	Female Right Angle								
PCB Mount		Solder	Thru Hole	PE51240	$37.79	$35.90	$34.01	$32.50	83
	Female Right Angle, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .531 inch Hole Spacing	PE4317	$41.79	$39.70	$37.61	$35.94	84
	Female Right Angle, Bulkhead Mount								
Terminal		Solder	Solder Cup with .361 inch D Hole	PE4055	$35.59	$33.81	$32.03	$30.61	85

Reverse Polarity BNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	PE-SR402AL, PE-SR402FL, RG402	PE4722	$30.99	$29.44	$27.89	$26.65	86
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4719	$47.99	$45.59	$43.19	$41.27	87
			RG178, RG196	PE4721	$35.19	$33.43	$31.67	$30.26	88
			RG213, RG214, RG8, RG9, RG225, RG393, RG215	PE4711	$47.99	$45.59	$43.19	$41.27	89
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4714	$47.39	$45.02	$42.65	$40.76	90
			RG59*, RG62*	PE4717	$19.79	$18.80	$17.81	$17.02	91
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4720	$32.39	$30.77	$29.15	$27.86	92
			RG213, RG8	PE4712	$38.39	$36.47	$34.55	$33.02	93
			RG214, RG9, RG225, RG393	PE4713	$41.19	$39.13	$37.07	$35.42	94
			RG55, RG141, RG142, RG223, RG400	PE4715	$19.79	$18.80	$17.81	$17.02	95

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

Reverse Polarity BNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Crimp/Solder	RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4716	$23.59	$22.41	$21.23	$20.29	96
			RG59*, RG62*	PE4718	$22.39	$21.27	$20.15	$19.26	97
	Male, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .531 inch Hole Spacing	PE4762	$31.99	$30.39	$28.79	$27.51	98
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188	PE4732	$33.19	$31.53	$29.87	$28.54	99
			RG213, RG214, RG8, RG9, RG225, RG393, RG215	PE4727	$59.99	$56.99	$53.99	$51.59	1
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4728	$32.99	$31.34	$29.69	$28.37	2
		Crimp/Solder	RG174, RG316, RG188	PE4733	$32.19	$30.58	$28.97	$27.68	3
			RG55, RG141, RG142, RG223, RG400	PE4729	$32.79	$31.15	$29.51	$28.20	4
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4730	$39.19	$37.23	$35.27	$33.70	5
	Female								
Cable Connectors		Clamp/Solder	PE-SR402AL, PE-SR402FL, RG402	PE4744	$31.59	$30.01	$28.43	$27.17	6
			PE-SR405AL, PE-SR405FL, RG405	PE4745	$31.99	$30.39	$28.79	$27.51	7
			RG174, RG316, RG188	PE4741	$39.79	$37.80	$35.81	$34.22	8
			RG178, RG196	PE4743	$39.79	$37.80	$35.81	$34.22	9
			RG213, RG214, RG8, RG9, RG225, RG393	PE4735	$49.39	$46.92	$44.45	$42.48	10
			RG55, RG58, RG141, RG142, RG223, RG400	PE4736	$47.99	$45.59	$43.19	$41.27	11
		Crimp/Solder	RG174, RG316, RG188	PE4742	$33.99	$32.29	$30.59	$29.23	12
			RG188-DS, RG316-DS	PE45182	$29.99	$28.49	$26.99	$25.79	13
			RG55, RG141, RG142, RG223, RG400	PE4737	$29.99	$28.49	$26.99	$25.79	14
			RG58	PE4738	$34.59	$32.86	$31.13	$29.75	15
			RG59*, RG62*	PE4739	$32.79	$31.15	$29.51	$28.20	16
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	PE-SR405AL, PE-SR405FL, RG405 with .480 inch D Hole	PE4755	$33.19	$31.53	$29.87	$28.54	17
			RG174, RG316, RG188 with .480 inch D Hole	PE4751	$30.39	$28.87	$27.35	$26.14	18
			RG55, RG58, RG141, RG142, RG223, RG400 with .480 inch D Hole	PE4746	$50.99	$48.44	$45.89	$43.85	19
			RG59*, RG62* with .480 inch D Hole	PE4749	$44.99	$42.74	$40.49	$38.69	20
		Crimp/Solder	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100A-FR, PE-C100, PE-B100 with .480 inch D Hole	PE4752	$36.39	$34.57	$32.75	$31.30	21
			RG55, RG142, RG223, RG400 with .480 inch D Hole	PE4747	$33.19	$31.53	$29.87	$28.54	22
			RG58, RG141 with .480 inch D Hole	PE4748	$34.99	$33.24	$31.49	$30.09	23
Terminal		Solder	Solder Cup with .350 inch D Hole	PE4758	$19.59	$18.61	$17.63	$16.85	24
			Solder Cup with .410 inch D Hole	PE4757	$21.39	$20.32	$19.25	$18.40	25
			Solder Cup with .480 inch D Hole	PE4764	$36.99	$35.14	$33.29	$31.81	26
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .500 inch Hole Spacing	PE4763	$32.59	$30.96	$29.33	$28.03	27
			Solder Cup with .500 inch Threaded Hole Spacing	PE4756	$32.59	$30.96	$29.33	$28.03	28
	Female Right Angle, Bulkhead Mount								
Terminal		Solder	Solder Cup with .361 inch D Hole	PE4759	$56.99	$54.14	$51.29	$49.01	29

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

C Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	RG14, RG217	PE4951	$79.99	$75.99	$71.99	$68.79	30
			RG174, RG316, RG188	PE4953	$46.79	$44.45	$42.11	$40.24	31
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4243	$83.99	$79.79	$75.59	$72.23	32
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4950	$73.99	$70.29	$66.59	$63.63	33
			RG218	PE4954	$117.99	$112.09	$106.19	$101.47	34
			RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE4242	$64.99	$61.74	$58.49	$55.89	35
			RG59*, RG62*, RG71	PE4952	$64.99	$62.39	$60.44	$59.14	36
		Crimp/Solder	RG213, RG8	PE4518	$46.79	$44.45	$42.11	$40.24	37
			RG214, RG9, RG225, RG393	PE4375	$35.59	$33.81	$32.03	$30.61	38
			RG55, RG141, RG142, RG223, RG400	PE4445	$37.19	$35.33	$33.47	$31.98	39
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4517	$49.39	$46.92	$44.45	$42.48	40
	Male, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .718 inch Hole Spacing	PE44096	$88.99	$84.54	$80.09	$76.53	41
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4244	$87.99	$83.59	$79.19	$75.67	42
			RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE4957	$117.99	$112.09	$106.19	$101.47	43
		Crimp/Solder	PE-P195, PE-C195, RG58, RG141, RG303, .195 inch, LMR-195	PE4959	$117.99	$112.09	$106.19	$101.47	44
			RG213, RG8	PE4955	$93.99	$89.29	$84.59	$80.83	45
			RG214, RG9, RG225, RG393	PE4949	$109.99	$104.49	$98.99	$94.59	46
			RG55, RG141, RG142, RG223, RG400	PE4958	$89.99	$85.49	$80.99	$77.39	47
	Female								
Cable Connectors		Clamp/Solder	RG14, RG217	PE4963	$89.99	$85.49	$80.99	$77.39	48
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4960	$72.99	$69.34	$65.69	$62.77	49
			RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE4961	$96.99	$92.14	$87.29	$83.41	50
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG214, RG213, RG393, RG8, RG225, RG11*, RG216*, RG144*, RG215, RG9 with .720 inch D Hole	PE4964	$86.99	$82.64	$78.29	$74.81	51
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, LMR-400, PE-C195, PE-P195 with .596 inch D Hole	PE44099	$91.99	$87.39	$82.79	$79.11	52
			RG58, RG55, RG141, RG142, RG223, RG400 with .720 inch D Hole	PE4965	$103.99	$98.79	$93.59	$89.43	53
Terminal		Solder	Solder Cup with .720 inch D Hole	PE4240	$68.99	$66.23	$64.16	$62.78	54
			Solder Cup with .720 inch D Hole	PE4972	$95.99	$91.19	$86.39	$82.55	55
			Turret with .350 inch D Hole	PE4973	$101.99	$96.89	$91.79	$87.71	56
	Female, 4 Hole Flange Mount								
Cable Connectors		Clamp/Solder	RG213, RG214, RG393, RG11*	PE4CO1013	$94.99	$90.24	$85.49	$81.69	57
			RG214, RG213, RG393, RG8, RG225, RG11*, RG216*, RG144*, RG215, RG9 with .718 inch Hole Spacing	PE4967	$103.99	$98.79	$93.59	$89.43	58
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, LMR-400, PE-C195, PE-P195 with .718 inch Hole Spacing	PE4969	$75.99	$72.19	$68.39	$65.35	59
		Crimp/Solder	RG214, RG9, RG225, RG393 with .718 inch Hole Spacing	PE4374	$87.99	$83.59	$79.19	$75.67	60
Terminal		Solder	Solder Cup with .718 inch Hole Spacing	PE4241	$31.99	$30.39	$28.79	$27.51	61

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

D-Sub Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE4808	$20.99	$19.94	$18.89	$18.05	62
		Solder/Solder	RG180, RG195, PE-B150	PE4815	$24.79	$23.55	$22.31	$21.32	63
			RG58, RG141, RG303	PE4812	$17.39	$16.52	$15.65	$14.96	64
	Plug Right Angle								
Cable Connectors		Solder/Solder	PE-SR405AL, PE-SR405FL, RG405	PE44038	$28.19	$27.06	$26.22	$25.65	65
			RG55, RG142, RG223, RG400	PE44036	$18.39	$17.47	$16.55	$15.82	66
	Receptacle								
Cable Connectors		Crimp/Solder	PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE4800	$20.99	$19.94	$18.89	$18.05	67
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE4801	$22.99	$21.84	$20.69	$19.77	68
		Solder/Solder	RG180, RG195	PE4807	$11.39	$10.82	$10.25	$9.80	69
			RG55, RG142, RG223, RG400	PE4838	$17.59	$16.71	$15.83	$15.13	70
			RG58, RG141, RG303	PE4804	$17.99	$17.09	$16.19	$15.47	71
	Receptacle Right Angle								
Cable Connectors		Crimp/Solder	RG58, RG141, RG303	PE4816	$33.59	$32.25	$31.24	$30.57	72

FAKRA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Beige Color	PE45404I	$7.49	$7.12	$6.74	$6.44	73
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Black Color	PE45404A	$6.69	$6.36	$6.02	$5.75	74
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Blue Color	PE45404C	$7.49	$7.12	$6.74	$6.44	75
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Bordeaux Color	PE45404D	$7.49	$7.12	$6.74	$6.44	76
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Curry Color	PE45404K	$7.49	$7.12	$6.74	$6.44	77
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Violet Color	PE45404H	$7.49	$7.12	$6.74	$6.44	78
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Water Blue Color	PE45404Z	$7.49	$7.12	$6.74	$6.44	79
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with White Color	PE45404B	$7.59	$7.06	$6.53	$6.07	80
PCB Mount		Solder	Thru Hole with Beige Color	PE44649I	$6.39	$6.07	$5.75	$5.50	81
			Thru Hole with Black Color	PE44649A	$8.29	$7.88	$7.46	$7.13	82
			Thru Hole with Blue Color	PE44649C	$8.09	$7.69	$7.28	$6.96	83
			Thru Hole with Bordeaux Color	PE44649D	$4.53	$4.30	$4.08	$3.90	84
			Thru Hole with Curry Color	PE44649K	$3.97	$3.77	$3.57	$3.41	85
			Thru Hole with Violet Color	PE44649H	$3.97	$3.77	$3.57	$3.41	86
			Thru Hole with Water Blue Color	PE44649Z	$8.39	$7.97	$7.55	$7.22	87
			Thru Hole with White Color	PE44649B	$3.97	$3.77	$3.57	$3.41	88
	Plug Right Angle								
PCB Mount		Solder	Thru Hole with Beige Color	PE44651I	$8.39	$7.97	$7.55	$7.22	89
			Thru Hole with Black Color	PE44651A	$11.39	$10.82	$10.25	$9.80	90
			Thru Hole with Blue Color	PE44651C	$11.39	$10.82	$10.25	$9.80	91
			Thru Hole with Bordeaux Color	PE44651D	$10.19	$9.68	$9.17	$8.76	92
			Thru Hole with Curry Color	PE44651K	$8.98	$8.53	$8.08	$7.72	93
			Thru Hole with Violet Color	PE44651H	$8.39	$7.97	$7.55	$7.22	94
			Thru Hole with Water Blue Color	PE44651Z	$10.39	$9.87	$9.35	$8.94	95
			Thru Hole with White Color	PE44651B	$6.79	$6.45	$6.11	$5.84	96

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

FAKRA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Jack								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Beige Color	PE44646I	$8.58	$8.15	$7.72	$7.38	97
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Black Color	PE44646A	$9.69	$9.21	$8.72	$8.33	98
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Blue Color	PE44646C	$9.69	$9.21	$8.72	$8.33	99
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Bordeaux Color	PE44646D	$8.39	$7.97	$7.55	$7.22	1
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Curry Color	PE44646K	$9.69	$9.21	$8.72	$8.33	2
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Violet Color	PE44646H	$9.69	$9.21	$8.72	$8.33	3
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Water Blue Color	PE44646Z	$8.89	$8.45	$8.00	$7.65	4
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with White Color	PE44646B	$8.79	$8.35	$7.91	$7.56	5
			RG188-DS, RG316-DS with Black Color	PE45176	$7.39	$7.02	$6.65	$6.36	6
			RG316-DS, RG188-DS with Water Blue Color	PE45176Z	$6.99	$6.50	$6.01	$5.59	7
	Jack Right Angle								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Beige Color	PE44648I	$6.79	$6.45	$6.11	$5.84	8
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Black Color	PE44648A	$11.79	$11.20	$10.61	$10.14	9
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Blue Color	PE44648C	$11.79	$11.20	$10.61	$10.14	10
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Bordeaux Color	PE44648D	$9.39	$8.92	$8.45	$8.08	11
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Curry Color	PE44648K	$10.59	$10.06	$9.53	$9.11	12
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Violet Color	PE44648H	$9.39	$8.92	$8.45	$8.08	13
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Water Blue Color	PE44648Z	$11.39	$10.82	$10.25	$9.80	14
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with White Color	PE44648B	$11.79	$11.20	$10.61	$10.14	15
PCB Mount		Solder	Thru Hole with Beige Color	PE44650I	$6.79	$6.45	$6.11	$5.84	16
			Thru Hole with Black Color	PE44650A	$6.49	$6.17	$5.84	$5.58	17
			Thru Hole with Blue Color	PE44650C	$8.09	$7.69	$7.28	$6.96	18
			Thru Hole with Bordeaux Color	PE44650D	$6.79	$6.45	$6.11	$5.84	19
			Thru Hole with Violet Color	PE44650H	$5.69	$5.41	$5.12	$4.89	20
			Thru Hole with Water Blue Color	PE44650Z	$11.79	$11.20	$10.61	$10.14	21
			Thru Hole with White Color	PE44650B	$9.29	$8.83	$8.36	$7.99	22

FME Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188	PE44297	$15.99	$15.19	$14.39	$13.75	23
			RG55, RG142, RG223, RG400	PE44296	$14.39	$13.67	$12.95	$12.38	24
			RG58	PE44295	$17.59	$16.71	$15.83	$15.13	25
	Plug, Bulkhead Mount								
Terminal		Solder	Solder Cup with .350 inch D Hole	PE44149	$11.19	$10.63	$10.07	$9.62	26
	Jack								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188	PE44148	$16.39	$15.57	$14.75	$14.10	27
			RG55, RG142, RG223, RG400	PE44147	$11.79	$11.20	$10.61	$10.14	28
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE44146	$13.39	$12.72	$12.05	$11.52	29

Connectors

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

GR874 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Sexless								
Cable Connectors		Accessories		PE4348	$61.99	$58.89	$55.79	$53.31	30
		Crimp/Solder	RG214, RG9, RG225, RG393	PE4352	$113.99	$108.29	$102.59	$98.03	31
			RG55, RG58, RG141, RG142, RG223, RG400	PE4233	$36.39	$34.57	$32.75	$31.30	32

HN Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	See Web for Volume Pricing	ROW
	Male						
Cable Connectors		Clamp/Solder	RG14, RG217	PE4475	$60.99		33
			RG17, RG218, RG219	PE4476	$165.99		34
			RG213, RG214, RG8, RG9, RG225, RG393	PE4182	$35.39		35
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4198	$47.19		36
			RG59*, RG62*, RG71	PE4479	$72.99		37
		Crimp/Solder	RG213, RG215, RG8	PE4473	$53.99		38
			RG214, RG9, RG225, RG393	PE4474	$56.99		39
			RG55, RG142, RG223, RG400, RG141	PE4477	$50.99		40
			RG58, RG141	PE4478	$44.99		41
	Male Right Angle						
Cable Connectors		Clamp/Solder	RG14, RG217	PE45307	$97.99	See Web for Volume Pricing	42
			RG213, RG8, RG393, RG225, RG214, RG393, RG9	PE4230	$73.99		43
			RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE4480	$98.99		44
	Female						
Cable Connectors		Clamp/Solder	RG213, RG8, RG225, RG214, RG393	PE4229	$75.99		45
			RG401, PE-SR401AL, PE-SR401FL	PE4229-401	$75.99		46
	Female, Bulkhead Mount						
Terminal		Solder	Turret with .765 inch DD Hole	PE4481	$74.99		47
	Female, 4 Hole Flange Mount						
Terminal		Field Replaceable	Slotted Contact	PE44718	$75.99		48
		Solder	Solder Cup with .906 inch Hole Spacing	PE4183	$40.79		49

LC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	See Web for Volume Pricing	ROW
	Male						
Cable Connectors		Clamp/Solder	RG14, RG217	PE4563	$259.99	See Web for Volume Pricing	50
			RG213, RG214, RG8, RG9, RG225, RG393, RG215	PE4564	$205.99		51
			RG218, RG219, RG17	PE4323	$275.99		52
	Male Right Angle						
Cable Connectors		Clamp/Solder	RG14, RG217	PE44448	$415.99		53
			RG213, RG214, RG8, RG9, RG225, RG393, RG215	PE44447	$317.99		54

Connectors

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

LC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	PRICE See Web for Volume Pricing	ROW
	Female						
Cable Connectors		Clamp/Solder	RG17, RG218, RG219	PE44451	$343.99	See Web for Volume Pricing	55
			RG213, RG214, RG8, RG9, RG225, RG393, RG215	PE44450	$267.99		56
	Female, 4 Hole Flange Mount						
Terminal		Solder	Pin	PE45519	$223.99		57
			Pin with 1.44 inch Hole Spacing	PE4192	$131.99		58

MC-Card Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188	PE44309	$14.59	$13.86	$13.13	$12.55	59
			RG178, RG196	PE44310	$14.59	$13.86	$13.13	$12.55	60
			RG188-DS, RG316-DS	PE45169	$14.39	$13.67	$12.95	$12.38	61
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE44308	$17.79	$16.90	$16.01	$15.30	62
			RG178, RG196	PE44311	$19.59	$18.61	$17.63	$16.85	63
			RG188-DS, RG316-DS	PE45168	$15.39	$14.62	$13.85	$13.24	64

MCX Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG178, RG196	PE4552	$24.79	$23.55	$22.31	$21.32	65
			RG188-DS, RG316-DS	PE4878	$17.79	$16.90	$16.01	$15.30	66
			RG316, RG174, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4551	$15.99	$15.19	$14.39	$13.75	67
			RG55, RG141, RG142, RG223, RG400	PE4881	$40.39	$38.77	$37.56	$36.75	68
			RG58	PE4880	$31.39	$30.13	$29.19	$28.56	69
		Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE4876	$30.99	$29.44	$27.89	$26.65	70
PCB Mount			Surface Mount	PE44613	$21.39	$20.32	$19.25	$18.40	71
			Thru Hole with .200 inch x .052 inch Hole Spacing	PE4559	$27.39	$26.02	$24.65	$23.56	72
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4553	$21.59	$20.51	$19.43	$18.57	73
			RG178, RG196	PE4554	$23.79	$22.60	$21.41	$20.46	74
			RG188-DS, RG316-DS	PE4879	$21.39	$20.32	$19.25	$18.40	75
			RG55, RG142, RG223, RG400	PE4883	$21.59	$20.51	$19.43	$18.57	76
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4882	$26.79	$25.45	$24.11	$23.04	77
		Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE4877	$36.39	$34.57	$32.75	$31.30	78
		Solder/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44698	$11.79	$11.20	$10.61	$10.14	79
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE44830	$22.39	$21.49	$20.82	$20.37	80

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

MCX Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Jack								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE4562	$30.19	$28.68	$27.17	$25.96	81
			RG178, RG196	PE4884	$38.39	$36.47	$34.55	$33.02	82
			RG188-DS, RG316-DS	PE4885	$25.19	$23.93	$22.67	$21.66	83
PCB Mount		Solder	.042 inch End Launch	PE4893	$29.99	$28.49	$26.99	$25.79	84
			.062 inch End Launch	PE4892	$17.59	$16.71	$15.83	$15.13	85
			End Launch	PE44661	$26.59	$25.26	$23.93	$22.87	86
			Surface Mount	PE44660	$39.99	$37.99	$35.99	$34.39	87
			Surface Mount	PE4889	$20.59	$19.56	$18.53	$17.71	88
			Thru Hole with .200 inch x .052 inch Hole Spacing	PE4555	$17.39	$16.52	$15.65	$14.96	89
			Thru Hole with .200 inch x .067 inch Hole Spacing	PE44303	$21.99	$20.89	$19.79	$18.91	90
	Jack, Bulkhead Mount								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch with .177 inch D Hole	PE4887	$29.19	$27.73	$26.27	$25.10	91
			RG188-DS, RG316-DS with .177 inch D Hole	PE4888	$22.59	$21.46	$20.33	$19.43	92
Terminal		Solder	Turret with .177 inch D Hole	PE4561	$24.79	$23.55	$22.31	$21.32	93
	Jack, 2 Hole Flange Mount								
Terminal		Solder	Pin with .328 inch Hole Spacing	PE4894	$32.99	$31.34	$29.69	$28.37	94
			Solder Cup with .328 inch Hole Spacing	PE4891	$34.99	$33.24	$31.49	$30.09	95
	Jack Right Angle								
PCB Mount		Solder	Surface Mount	PE4890	$28.39	$26.97	$25.55	$24.42	96
			Thru Hole with .200 inch x .052 inch Hole Spacing	PE45274	$19.59	$18.61	$17.63	$16.85	97
			Thru Hole with .200 inch x .052 inch Hole Spacing	PE4556	$21.19	$20.13	$19.07	$18.22	98
	Jack Right Angle, Bulkhead Mount								
Terminal		Solder	Turret with .177 inch D Hole	PE4560	$58.99	$56.04	$53.09	$50.73	99

MHV Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188	PE4494	$22.99	$21.84	$20.69	$19.77	1
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4299	$41.59	$39.51	$37.43	$35.77	2
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4076	$25.19	$23.93	$22.67	$21.66	3
			RG59*, RG62*, RG71	PE4098	$20.39	$19.37	$18.35	$17.54	4
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4933	$53.99	$51.29	$48.59	$46.43	5
			RG213, RG8	PE4493	$41.99	$39.89	$37.79	$36.11	6
			RG214, RG9, RG225, RG393	PE4350	$47.39	$45.02	$42.65	$40.76	7
			RG55, RG141, RG142, RG223, RG400	PE4657	$26.59	$25.26	$23.93	$22.87	8
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4093	$30.79	$29.25	$27.71	$26.48	9
			RG59*, RG62*, RG71	PE4075	$25.59	$24.31	$23.03	$22.01	10
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188	PE4710	$44.99	$42.74	$40.49	$38.69	11
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393	PE4709	$79.99	$75.99	$71.99	$68.79	12
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4226	$45.79	$43.50	$41.21	$39.38	13
			RG59*, RG62*, RG71	PE4227	$42.59	$40.46	$38.33	$36.63	14
	Female								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188	PE44104	$37.19	$35.33	$33.47	$31.98	15
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4225	$33.79	$32.10	$30.41	$29.06	16
			RG59*, RG62*, RG71	PE4181	$31.59	$30.01	$28.43	$27.17	17

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

MHV Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	See Web for Volume Pricing			ROW
	Female								
Cable Connectors		Crimp/Solder	PE-P195, PE-C195, RG58, RG141, RG303, .195 inch, LMR-195	PE44102	$38.19				18
			RG55, RG141, RG142, RG223, RG400	PE44100	$35.79				19
			RG59*, RG62*	PE44103	$46.39				20
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188	PE44111	$62.99		See Web for Volume Pricing		21
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393	PE44105	$83.99				22
			RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE44106	$65.99				23
			RG59*, RG62*, RG71	PE44109	$61.99				24
		Crimp/Solder	RG55, RG141, RG142, RG223, RG400	PE44107	$38.99				25
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE44108	$52.99				26
			RG59*, RG62*, RG71	PE44110	$65.99				27
Terminal		Solder	Solder Cup	PE44896	$145.99				28
			Solder Cup with .380 inch DD Hole	PE4193	$32.59				29
			Solder Cup with .380 inch DD Hole	PE4311	$61.99				30
			Solder Cup with .480 inch D Hole	PE4495	$61.99				31
			Turret with .537 inch D Hole	PE4312	$50.99				32
	Female, 4 Hole Flange Mount								
Cable Connectors		Clamp/Solder	RG214, RG213, RG393, RG8, RG225, RG11*, RG216*, RG144*, RG215, RG9 with .718 inch Hole Spacing	PE44112	$73.99				33
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, LMR-400, PE-C195, PE-P195 with .500 inch Threaded Hole Spacing	PE4313	$61.99				34
			RG59*, RG62*, RG71 with .500 inch Threaded Hole Spacing	PE4314	$65.99				35
Terminal		Solder	Solder Cup	PE45035	$72.99				36
			Solder Cup with .500 inch Threaded Hole Spacing	PE4228	$42.39				37

Mini SMP Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
PCB Mount		Solder	Edge Launch	PE44969	$37.39	$35.52	$33.65	$32.16	38
			End Launch	PE44490	$34.19	$32.48	$30.77	$29.40	39
			Surface Mount	PE44489	$40.39	$38.37	$36.35	$34.74	40
			Thru Hole	PE44970	$69.99	$66.49	$62.99	$60.19	41
	Male Right Angle								
PCB Mount		Solder	Surface Mount	PE44968	$84.99	$80.74	$76.49	$73.09	42
	Male, Solder								
Terminal		Solder	Pin	PE44973	$51.99	$49.39	$46.79	$44.71	43
	Female								
Cable Connectors		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44491	$50.99	$48.44	$45.89	$43.85	44
			PE-047SR, PE-SR047FL	PE44971	$58.99	$56.04	$53.09	$50.73	45
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44492	$49.99	$47.49	$44.99	$42.99	46
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44974	$46.79	$44.45	$42.11	$40.24	47
	Female Right Angle								
Cable Connectors		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44493	$65.99	$62.69	$59.39	$56.75	48
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44494	$58.99	$56.04	$53.09	$50.73	49
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44972	$75.99	$72.19	$68.39	$65.35	50

Connectors

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

Mini UHF Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188	PE44090	$16.59	$15.76	$14.93	$14.27	51
			RG55, RG141, RG142, RG223, RG400	PE44088	$14.99	$14.24	$13.49	$12.89	52
			RG55, RG141, RG142, RG223, RG400	PE4521	$9.29	$8.83	$8.36	$7.99	53
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4342	$9.29	$8.83	$8.36	$7.99	54
	Female								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188	PE44085	$6.69	$6.36	$6.02	$5.75	55
			RG55, RG141, RG142, RG223, RG400	PE44083	$14.39	$13.67	$12.95	$12.38	56
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE44084	$18.79	$17.85	$16.91	$16.16	57
	Female, Bulkhead Mount								
Cable Connectors		Crimp/Solder	.195 inch, RG58, RG141, RG303, LMR-195, LMR-195-FR, PE-C195, PE-P195 with .410 inch D Hole	PE44087	$21.19	$20.13	$19.07	$18.22	58
			RG55, RG141, RG142, RG223, RG400 with .410 inch D Hole	PE44086	$17.59	$16.71	$15.83	$15.13	59
PCB Mount		Solder	Thru Hole with .380 inch Diameter	PE44092	$14.99	$14.24	$13.49	$12.89	60
Terminal			Solder Cup with .350 inch D Hole	PE44089	$11.39	$10.82	$10.25	$9.80	61
			Solder Cup with .350 inch D Hole	PE4644	$8.99	$8.54	$8.09	$7.73	62
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .437 inch Hole Spacing	PE44091	$15.19	$14.43	$13.67	$13.06	63

MMBX Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	See Web for Volume Pricing	ROW
	Plug						
Cable Connectors		Crimp/Solder	RG178, RG196	PE45250	$16.19	See Web for Volume Pricing	64
			RG316, RG174	PE45251	$21.19		65
			RG316-DS, RG188-DS	PE45252	$14.39		66
		Solder/ Non-Solder Contact	RG405, PE-SR405FL, PE-SR405FLJ	PE45253	$18.79		67
PCB Mount		Solder/Solder	Surface Mount	PE45259TR1	$23.19		68
			Surface Mount	PE45259TR750	$11,300.00		69
	Plug Right Angle						
Cable Connectors		Crimp/Solder	RG178, RG196	PE45254	$21.39		70
			RG316, RG174	PE45255	$21.99		71
			RG316-DS, RG188-DS	PE45256	$21.39		72
		Solder/Solder	RG405, PE-SR405FL, PE-SR405FLJ	PE45257	$21.39		73
	Jack						
PCB Mount		Solder	Edge Launch	PE45261	$21.19	See Web for Volume Pricing	74
			Surface Mount	PE45262TR1	$14.39		75
			Surface Mount	PE45262TR750	$6,980.00		76
			Through Hole	PE45265TR1	$17.39		77
			Through Hole	PE45265TR500	$5,850.00		78
	Jack, Thread-In						
Terminal		Solder	Pin	PE45267	$16.59		79

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

MMCX Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4896	$22.39	$21.27	$20.15	$19.26	80
			RG178, RG196	PE44645	$23.19	$22.03	$20.87	$19.94	81
			RG178, RG196	PE4897	$21.39	$20.32	$19.25	$18.40	82
			RG188-DS, RG316-DS	PE44874	$24.39	$23.17	$21.95	$20.98	83
		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44456	$27.59	$26.21	$24.83	$23.73	84
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44453	$25.79	$24.50	$23.21	$22.18	85
PCB Mount			End Launch	PE44663	$29.39	$27.92	$26.45	$25.28	86
			Thru Hole with .100 inch x .031 inch Hole Spacing	PE4905	$32.99	$31.34	$29.69	$28.37	87
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4898	$14.99	$14.24	$13.49	$12.89	88
			RG178, RG196	PE4899	$24.79	$23.55	$22.31	$21.32	89
			RG316-DS, RG188-DS	PE44784	$27.59	$26.21	$24.83	$23.73	90
		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44457	$32.79	$31.15	$29.51	$28.20	91
		Solder/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44699	$11.59	$11.01	$10.43	$9.97	92
	Jack								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE4901	$21.99	$20.89	$19.79	$18.91	93
			RG178, RG196	PE4902	$21.99	$20.89	$19.79	$18.91	94
			RG316-DS, RG188-DS	PE44852	$24.39	$23.17	$21.95	$20.98	95
		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44459	$40.39	$38.37	$36.35	$34.74	96
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44458	$38.19	$36.28	$34.37	$32.84	97
PCB Mount			Surface Mount	PE44662	$27.19	$25.83	$24.47	$23.38	98
			Thru Hole with .100 inch x .031 inch Hole Spacing	PE4904	$18.39	$17.47	$16.55	$15.82	99
	Jack Right Angle								
PCB Mount		Solder	Thru Hole with .100 inch x .031 inch Hole Spacing	PE4903	$28.99	$27.54	$26.09	$24.93	1

Reverse Polarity MCX Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE44369	$32.79	$31.15	$29.51	$28.20	2
			RG178, RG196	PE44370	$31.99	$30.39	$28.79	$27.51	3
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG178, RG196	PE45051	$10.39	$9.97	$9.66	$9.45	4
			RG316, RG188, RG174	PE45050	$11.39	$10.82	$10.25	$9.80	5
	Jack, Bulkhead Mount								
Cable Connectors		Crimp/Solder	RG178, RG196 with .177 inch D Hole	PE44374	$38.99	$37.04	$35.09	$33.53	6
PCB Mount		Solder	End Launch with .177 inch D Hole	PE44377	$35.39	$33.62	$31.85	$30.44	7

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

Reverse Polarity MCX Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Jack Right Angle, Bulkhead Mount								
PCB Mount		Solder	Thru Hole with .177 inch D Hole	PE44376	$39.59	$37.61	$35.63	$34.05	8

N Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp	7/8 inch Annular, 7/8 inch Helical, 7/8 inch Superflexible, 7/8 inch Flexible	PE44976	$74.99	$71.24	$67.49	$64.49	9
		Clamp/ Non-Solder Contact	1/2 inch Helical, 1/2 inch Superflexible, PE-1/2 Helical, PE-1/2SFHC	PE44729	$59.99	$56.99	$53.99	$51.59	10
			1/4 inch Superflexible, PE-1/4SFHC	PE44726	$75.99	$72.19	$68.39	$65.35	11
			LMR-400, PE-C400, PE-B400, PE-B405	EZ-400-NMC-2-D	$26.79	$26.79	$26.79	$26.79	12
			LMR-600, PE-C600	EZ-600-NMC-2-D	$25.19	$25.19	$25.19	$25.19	13
			PE-1/2FAC, 1/2 inch Flexible, 1/2 inch Annular	PE44735	$53.99	$51.29	$48.59	$46.43	14
		Clamp/Solder	PE-C300	PE44045	$28.99	$27.54	$26.09	$24.93	15
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE4133	$33.59	$32.25	$31.24	$30.57	16
			PE-C500, LMR-500	PE44046	$47.59	$45.21	$42.83	$40.93	17
			PE-C600, .600 inch, LMR-600	PE44349	$94.99	$90.24	$85.49	$81.69	18
			PE-P142LL	PE44825	$58.99	$56.04	$53.09	$50.73	19
			PE-P160LL	PE45446	$105.99	$100.69	$95.39	$91.15	20
			PE-P300LL	PE44809	$93.99	$89.29	$84.59	$80.83	21
			PE-SR401AL, PE-SR401FL, RG401	PE4434	$27.59	$26.21	$24.83	$23.73	22
			PE-SR402AL, PE-SR402FL, RG402	PE4006	$27.59	$26.21	$24.83	$23.73	23
			PE-SR405AL, PE-SR405FL, RG405	PE4129	$27.19	$25.83	$24.47	$23.38	24
			RG14, RG217	PE4221	$37.59	$35.71	$33.83	$32.33	25
			RG17, RG218, RG219	PE4433	$127.99	$121.59	$115.19	$110.07	26
			RG174, RG316, RG188	PE4224	$22.99	$21.84	$20.69	$19.77	27
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4062	$22.79	$21.65	$20.51	$19.60	28
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4081	$16.19	$15.38	$14.57	$13.92	29
			RG59*, RG62*, RG71	PE4331	$25.59	$24.31	$23.03	$22.01	30
		Clamp/Solder (Captive Contact)	RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4132	$22.79	$21.65	$20.51	$19.60	31
		Crimp/Crimp	PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE44520	$14.59	$13.86	$13.13	$12.55	32
			RG55, RG141, RG142, RG223, RG400	PE4042	$27.19	$25.83	$24.47	$23.38	33
		Crimp/ Non-Solder Contact	LMR-240, PE-C240, RG8X	EZ-240-NMH-X	$12.79	$12.79	$12.79	$12.79	34
			LMR-400, PE-C400	EZ-400-NMH-PL-X	$16.79	$16.79	$16.79	$16.79	35
			LMR-400, PE-C400, PE-B400, PE-B405	EZ-400-NMH-X	$15.19	$15.19	$15.19	$15.19	36
			LMR-600, PE-C600	EZ-600-NMH-X	$22.19	$22.19	$22.19	$22.19	37
		Crimp/Solder	LMR-195, PE-C195	TC-195-NMH-X	$13.59	$13.59	$13.59	$13.59	38
			LMR-200, PE-C200	TC-200-NMH-X	$18.19	$0.89	Call	Call	39
			LMR-240, PE-C240	TC-240-NMH-X	$15.59	$15.59	$15.59	$15.59	40
			LMR-400, PE-C400, PE-B405	TC-400-NMH-X	$15.19	$15.19	$15.19	$15.19	41
			LMR-600, PE-C600	TC-600-NMH-X	$20.79	$20.79	$20.79	$20.79	42
			PE-B400, PE-B405, PE-C400, LMR-400, .400 inch	PE4550	$20.39	$19.37	$18.35	$17.54	43
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44521	$21.39	$20.32	$19.25	$18.40	44
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44522	$25.19	$23.93	$22.67	$21.66	45
			PE-C600, LMR-600, LMR-600-DB, .600 inch	PE44454	$42.79	$41.08	$39.79	$38.94	46
			PE-C600, LMR-600, LMR-600-DB, .600 inch	PE44523	$85.99	$81.69	$77.39	$73.95	47
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4429	$23.19	$22.03	$20.87	$19.94	48
			RG178, RG196	PE4647	$35.99	$34.19	$32.39	$30.95	49

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

N Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	PRICE See Web for Volume Pricing	ROW
	Male						
Cable Connectors		Crimp/Solder	RG213, RG215, RG8	PE4430	$26.59	See Web for Volume Pricing	50
			RG214, RG9, RG225, RG393	PE4048	$26.99		51
			RG223, RG142, RG400, RG55	PE44788	$22.39		52
			RG58, RG141, RG303, LMR-195, PE-C195, PE-P195, .195 inch	PE4329	$17.99		53
			RG59*, RG62*, RG71	PE4432	$22.99		54
			RG8X, PE-C240, .240 inch, B7808A, LMR-240	PE4344	$18.59		55
		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE4934	$43.99		56
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45664	$15.59		57
			PE-SR401AL, PE-SR401FL, RG401	PE4376	$60.99		58
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE4140	$32.79		59
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44701	$25.39		60
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE45002	$43.99		61
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44700	$24.19		62
			SPO-500, SPP-500-LLPL, SPF-500	TC-500-NM-LP	$12.19		63
			SPP-250-LLPL	PE45427	$32.79		64
			SPP-250-LLPL, SPF-250, SPO-250, 1/4" Superflexible, PE-1/4SFHC	TC-250-NM-LP	$15.19		65
			SPP-375-LLPL, SPO-375, SPF-375	TC-375-NM-LP	$15.19		66
			TFT-402, TFT-402-LF	TC-402-NM-LP	$15.99		67
		Threaded	VNA Test Cable	PE45505	$560.00		68
	Male, Bulkhead Mount						
Terminal		Solder	Solder Cup with .350 inch D Hole	PE4490	$54.99		69
			Solder Cup with .350 inch D Hole	PE4490BK	$53.99		70
			Solder Cup with .640 inch DD Hole	PE4489	$47.99		71
	Male, 4 Hole Flange Mount						
Terminal		Solder	Pin with .718 inch Hole Spacing	PE44653	$99.99		72
			Pin with .718 inch Hole Spacing	PE4491	$42.79		73
			Solder Cup with .718 inch Hole Spacing	PE4131	$22.19		74
	Male Right Angle						
Cable Connectors		Clamp/ Non-Solder Contact	1/2 inch Helical, 1/2 inch Superflexible, PE-1/2 Helical, PE-1/2SFHC	PE44554	$103.99	See Web for Volume Pricing	75
		Clamp/Solder	PE-B400, PE-B405, PE-C400	PE4938	$33.79		76
			PE-P142LL	PE44816	$185.99		77
			PE-P160LL	PE45448	$167.99		78
			PE-P300LL	PE45225	$187.99		79
			PE-SR401AL, PE-SR401FL, RG401	PE4935	$38.99		80
			RG213, RG8, RG215, RG225, RG214, RG393	PE4136	$35.39		81
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4135	$30.99		82
		Crimp/ Non-Solder Contact	LMR-400, PE-C400, PE-B400, PE-B405	EZ-400-NMH-RA-X	$30.19		83
			LMR-600, PE-C600	EZ-600-NMH-RA-X	$30.99		84
		Crimp/Solder	LMR-195, PE-C195	TC-195-NMH-RA-D	$15.59		85
			PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE44524	$50.99		86
			PE-C200, LMR-200	PE44844	$67.99		87
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44525	$71.99		88
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44526	$52.99		89
			PE-C600, LMR-600, LMR-600-DB, .600 inch	PE44527	$75.99		90
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE44675	$43.59		91
			RG213, RG8	PE4482	$49.39		92
			RG55, RG141, RG142, RG223, RG400	PE4484	$36.59		93
			RG58	PE4485	$32.59		94

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

N Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	PRICE See Web for Volume Pricing	ROW
	Male Right Angle						
Cable Connectors		Solder/Solder	LMR-400, PE-C400, PE-B405	TC-400-NMH-RA-D	$22.19	See Web for Volume Pricing	95
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45665	$19.19		96
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44703	$31.19		97
			PE-SR402AL, PE-SR402FL, RG402	PE4936	$46.59		98
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405	PE44702	$28.19		99
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405	PE4937	$33.79		1
			SPO-500, SPF-500	TC-SPO500-NM-RA-LP	$15.79		2
			SPP-250-LLPL	PE45428	$36.39		3
			SPP-250-LLPL, SPF-250, SPO-250, 1/4" Superflexible, PE-1/4SFHC	TC-250-NM-RA-LP	$18.19		4
			TFT-402, TFT-402-LF	TC-402-NM-RA-LP	$17.79		5
	Female						
Cable Connectors		Clamp/ Non-Solder Contact	1/2 inch Helical, 1/2 inch Superflexible, PE-1/2 Helical, PE-1/2SFHC	PE44731	$58.99	See Web for Volume Pricing	6
			1/4 inch Superflexible, PE-1/4SFHC	PE44727	$76.99		7
			7/8 inch annular	PE45036	$80.99		8
			7/8 inch Helical	PE45203	$65.99		9
			PE-1/2FAC, 1/2 inch Flexible, 1/2 inch Annular	PE44737	$56.99		10
		Clamp/Solder	1/2 inch Annular	PE44565	$107.99		11
			PE-B400, PE-B405, PE-C400, LMR-400, .400 inch	PE4372	$40.99		12
			PE-C600	PE44350	$117.99		13
			PE-P300LL	PE45245	$131.99		14
			PE-SR401AL, PE-SR401FL, RG401	PE4439	$31.79		15
			PE-SR402AL, PE-SR402FL, RG402	PE4138	$27.59		16
			PE-SR405AL, PE-SR405FL, RG405	PE4130	$24.39		17
			RG14, RG217	PE4645	$90.99		18
			RG17, RG218, RG219	PE4646	$101.99		19
			RG174, RG316, RG188	PE4437	$26.59		20
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4061	$25.39		21
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4072	$24.39		22
			RG59*, RG62*, RG71	PE4330	$23.79		23
		Clamp/Solder (Captive Contact)	RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4059	$39.99		24
		Crimp/Crimp	RG55, RG141, RG142, RG223, RG400	PE4134	$23.39		25
		Crimp/ Non-Solder Contact	LMR-600, PE-C600	EZ-600-NF-X	$25.19		26
		Crimp/Solder	LMR-400, PE-C400	TC-400-NF-X	$19.99		27
			PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE44532	$20.79		28
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44533	$22.79		29
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44534	$32.59		30
			PE-C600, LMR-600, LMR-600-DB, .600 inch	PE44535	$68.99		31
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4438	$30.99		32
			RG188-DS, RG316-DS	PE45172	$28.19		33
			RG213, RG8	PE4435	$21.39		34
			RG214, RG9, RG225, RG393	PE4191	$28.79		35
			RG223, RG142, RG400, RG55	PE44789	$27.79		36
			RG58	PE4436	$21.19		37
		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE4945	$50.99		38
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45666	$15.59		39
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44705	$32.99		40
			PE-SR402AL, PE-SR402FL, RG402	PE4652	$60.99		41
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405	PE44704	$44.99		42
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405	PE4653	$40.39		43

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

N Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	PRICE See Web for Volume Pricing	ROW
	Female						
Cable Connectors		Solder/Solder	SPO-375, SPF-375	TC-SPP375-NF-LP	$14.79	See Web for Volume Pricing	44
			SPP-250-LLPL	PE45426	$32.79		45
			TFT-402, TFT-402-LF	TC-402-NF-LP	$14.79		46
		Threaded	VNA Test Cable	PE45502	$497.99		47
PCB Mount		Solder	Thru Hole with .400 inch x .062 inch Hole Spacing	PE44396	$33.79		48
	Female, Bulkhead Mount						
Cable Connectors		Clamp/Solder	PE-B400, PE-B405, PE-C400 with .640 inch DD Hole	PE4943	$30.39	See Web for Volume Pricing	49
			PE-P142LL	PE44813	$125.99		50
			PE-P160LL	PE45447	$129.99		51
			PE-P300LL	PE44807	$147.99		52
			PE-SR401AL, PE-SR401FL, RG401 with .640 inch DD Hole	PE4942	$32.79		53
			PE-SR402AL, PE-SR402FL, RG402 with .640 inch DD Hole	PE4113	$25.59		54
			PE-SR405AL, PE-SR405FL, RG405, PE-SR405TN with .640 inch DD Hole	PE4443	$27.59		55
			RG174, RG316, RG188 with .640 inch DD Hole	PE4441	$29.39		56
			RG178 with .640 inch DD Hole	PE44633	$29.39		57
			RG188-DS, RG316-DS with .640 inch DD Hole	PE45173	$26.79		58
			RG214, RG213, RG393, RG8, RG225, RG11*, RG216*, RG144*, RG215, RG9 with .640 inch DD Hole	PE4223	$34.99		59
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, LMR-400, PE-C195, PE-P195 with .640 inch DD Hole	PE4114	$29.19		60
			RG59*, RG62* with .640 inch DD Hole	PE4297	$37.19		61
		Crimp/Crimp	RG55, RG142, RG223, RG400 with .640 inch DD Hole	PE4371	$28.99		62
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch with .640 inch DD Hole	PE4440	$23.79		63
		Crimp/ Non-Solder Contact	LMR-600, PE-C600	EZ-600-NF-BH	$43.99		64
		Crimp/Solder	.240 inch, RG8X, LMR-240, B7808A, LMR-240-DB, LMR-240-UF, PE-C240 with .640 inch DD Hole	PE44529	$21.59		65
			.400 inch, LMR-400, LMR-400-DB, LMR-400-UF, PE-B405, PE-C400, PE-B400 with .640 inch DD Hole	PE44530	$31.99		66
			LMR-200, PE-C200	PE45047	$30.39		67
			LMR-240, PE-C240	TC-240-NF-BH-X	$25.39		68
			PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch with .640 inch DD Hole	PE44528	$33.59		69
			PE-C600, LMR-600 with .640 inch DD Hole	PE44531	$60.99		70
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch with .640 inch DD Hole	PE4442	$35.79		71
			RG188-DS, RG316-DS	PE44877	$38.79		72
			RG213, RG8 with .640 inch DD Hole	PE4940	$40.59		73
			RG214, RG9, RG225, RG393 with .640 inch DD Hole	PE4941	$28.99		74
		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL with .640 inch DD Hole	PE4946	$44.99		75
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45667	$15.59		76
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402 with .640 inch DD Hole	PE44707	$28.99		77
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402 with .640 inch DD Hole	PE4654	$52.99		78
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44706	$31.19		79
			PE-SR405AL, PE-SR405FL, RG405 with .640 inch DD Hole	PE4655	$45.99		80
			SPP-250-LLPL	TC-SPP250-NF-BH-LP	$13.19		81
			TFT-402, TFT-402-LF	TC-402-NF-BH-LP	$15.99		82

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

N Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	PRICE See Web for Volume Pricing	ROW
PCB Mount		Solder	End Launch with .630 inch Diameter	PE44615	$39.59	See Web for Volume Pricing	83
			Thru Hole with .640 inch DD Hole	PE44397	$60.99		84
Terminal			Pin with .640 inch DD Hole	PE4139	$28.19		85
			Solder Cup with .380 inch Diameter	PE4488	$18.99		86
			Solder Cup with .640 inch DD Hole	PE4137	$40.19		87

N Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, 2 Hole Flange Mount								
Terminal		Solder	Pin with 1.0 inch Hole Spacing	PE44079	$63.99	$60.79	$57.59	$55.03	88
			Solder Cup with 1.0 inch Hole Spacing	PE44077	$36.79	$34.95	$33.11	$31.64	89
	Female, 4 Hole Flange Mount								
Cable Connectors		Clamp/Solder	PE-SR401AL, PE-SR401FL, RG401 with .718 inch Hole Spacing	PE44071	$32.59	$30.96	$29.33	$28.03	90
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402 with .718 inch Hole Spacing	PE44072	$32.79	$31.15	$29.51	$28.20	91
			PE-SR405AL, PE-SR405FL, RG405 with .718 inch Hole Spacing	PE44073	$32.39	$30.77	$29.15	$27.86	92
			RG174, RG316, RG188 with .718 inch Hole Spacing	PE44070	$25.19	$23.93	$22.67	$21.66	93
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, PE-C195, PE-P195 with .718 inch Hole Spacing	PE4141	$25.79	$24.50	$23.21	$22.18	94
		Clamp/Solder (Captive Contact)	RG214, RG213, RG393, RG8, RG225, RG11*, RG216*, RG144*, RG215, RG9 with .718 inch Hole Spacing	PE4060	$34.19	$32.48	$30.77	$29.40	95
		Crimp/Solder	.195 inch, RG58, RG141, RG303, LMR-195, LMR-195-FR, PE-C195, PE-P195 with .718 inch Hole Spacing	PE44069	$33.79	$32.10	$30.41	$29.06	96
			RG213, RG8 with .718 inch Hole Spacing	PE44065	$29.59	$28.11	$26.63	$25.45	97
			RG214, RG9, RG225, RG393 with .718 inch Hole Spacing	PE44066	$33.79	$32.10	$30.41	$29.06	98
			RG316, RG174, LMR-100	PE45133	$27.59	$26.21	$24.83	$23.73	99
			RG55, RG141, RG142, RG223, RG400 with .718 inch Hole Spacing	PE44068	$32.19	$30.58	$28.97	$27.68	1
Terminal		Field Replaceable	Slotted Contact	PE44721	$37.39	$35.52	$33.65	$32.16	2
			Slotted Contact	PE44722	$42.59	$40.46	$38.33	$36.63	3
		Solder	Pin with .340 inch Hole Spacing	PE4355	$30.99	$29.44	$27.89	$26.65	4
			Pin with .500 inch Hole Spacing	PE4444	$28.59	$27.16	$25.73	$24.59	5
			Pin with .718 inch Hole Spacing	PE4328	$27.79	$26.40	$25.01	$23.90	6
			Solder Cup	PE45085	$24.59	$23.36	$22.13	$21.15	7
			Solder Cup with .718 inch Hole Spacing	PE4487	$72.99	$69.34	$65.69	$62.77	8
			Tab with .718 inch Hole Spacing	PE4492	$46.39	$44.07	$41.75	$39.90	9
	Female, Press-In								
Terminal		Solder	Pin with .500 inch Diameter	PE44074	$37.59	$35.71	$33.83	$32.33	10
			Solder Cup with .500 inch Diameter	PE44076	$23.39	$22.22	$21.05	$20.12	11
			Tab with .500 inch Diameter	PE44075	$24.39	$23.17	$21.95	$20.98	12
	Female Right Angle, Bulkhead Mount								
PCB Mount		Solder	Thru Hole with .596 inch D Hole	PE44398	$36.59	$34.76	$32.93	$31.47	13
	Female Right Angle, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .718 inch Hole Spacing	PE4486	$59.99	$56.99	$53.99	$51.59	14

Connectors

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

Reverse Polarity N Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Crimp/Solder	PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44470	$45.99	$43.69	$41.39	$39.55	15
			RG213, RG8, RG215	PE44472	$45.59	$43.31	$41.03	$39.21	16
			RG214, RG393	PE44474	$37.79	$35.90	$34.01	$32.50	17
	Female								
Cable Connectors		Crimp/Solder	RG213, RG8	PE44478	$32.79	$31.15	$29.51	$28.20	18
			RG214, RG9, RG225, RG393	PE44477	$39.79	$37.80	$35.81	$34.22	19
			RG55, RG141, RG142, RG223, RG400	PE44475	$36.99	$35.14	$33.29	$31.81	20
			RG58	PE44476	$40.59	$38.56	$36.53	$34.91	21

N, 7mm, SC Torque Wrenches



Type	Bit Hex Size (in.)	Preset Torque (in.-lbs.)	Model No	1-9	10-24	25-49	50+	ROW
N, 7mm, SC	20 mm	14 in-lbs	PE5011-7	$361.99	$347.51	$336.65	$329.41	
		8.1 in-lbs	PE5019-5	$285.99	$271.69	$257.39	$245.95	
	3/4 inch	14 in-lbs	PE5019-4	$283.99	$269.79	$255.59	$244.23	
	13/16 inch	14 in-lbs	PE5019-8	$283.99	$269.79	$255.59	$244.23	

NEX10 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45668	$21.39	$20.32	$19.25	$18.40	22
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45672	$25.99	$24.69	$23.39	$22.35	23
			TFT-402, TFT-402-LF	TC-402-NX10M-LP	$23.19	$23.19	$23.19	$23.19	24
	Male Right Angle								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45669	$28.39	$26.97	$25.55	$24.42	25
			TFT-402, TFT-402-LF	TC-402-NX10M-RA-LP	$30.99	$30.99	$30.99	$30.99	26
	Female								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45670	$17.59	$16.71	$15.83	$15.13	27
	Female, Bulkhead Mount								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45671	$20.79	$19.75	$18.71	$17.88	28

NMO Mount Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Sexless								
Cable Connectors		Crimp/Solder	PE-C195, PE-P195, RG58, RG55, RG141, RG142, RG223, RG400, RG303, LMR-195	PE51021	$20.19	$19.18	$18.17	$17.36	29
			RG58, LMR-195	PE51167	$29.99	$28.49	$26.99	$25.79	30

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

QMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Crimp/Solder	LMR-200, PE-C200	PE45224	$19.39	$18.42	$17.45	$16.68	31
			PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE44503	$30.39	$28.87	$27.35	$26.14	32
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE44501	$37.79	$35.90	$34.01	$32.50	33
			RG55, RG142, RG223, RG400	PE44514	$26.59	$25.26	$23.93	$22.87	34
		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45682	$12.99	$12.34	$11.69	$11.17	35
			PE-SR405AL, PE-SR405FL, RG405	PE44495	$29.19	$27.73	$26.27	$25.10	36
			SPP-250-LLPL, SPO-250, SPF-250, and PE-1/4SFHC	PE45430	$27.59	$26.21	$24.83	$23.73	37
			TFT-402, TFT-402-LF	TC-402-QM-LP	$12.99	$12.99	$12.99	$12.99	38
	Male Right Angle								
Cable Connectors		Crimp/ Non-Solder Contact	LMR-240, PE-C240, LMR-240-UF	EZ-240-QM-RA-X	$21.19	$21.19	$21.19	$21.19	39
		Crimp/Solder	PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE44506	$36.99	$35.14	$33.29	$31.81	40
			RG174, RG316, RG188	PE45284	$31.19	$29.63	$28.07	$26.82	41
			RG316-DS, RG188-DS	PE44505	$40.39	$38.37	$36.35	$34.74	42
			RG55, RG142, RG223, RG400	PE44515	$38.79	$36.85	$34.91	$33.36	43
		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45683	$17.99	$17.09	$16.19	$15.47	44
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44498	$34.99	$33.24	$31.49	$30.09	45
			PE-SR405AL, PE-SR405FL, RG405	PE44497	$32.79	$31.15	$29.51	$28.20	46
			SPP-250-LLPL	PE45431	$30.39	$28.87	$27.35	$26.14	47
			TFT-402, TFT-402-LF	TC-402-QM-RA-LP	$17.79	$17.79	$17.79	$17.79	48
	Female								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45684	$12.59	$11.96	$11.33	$10.83	49
			SPP-250-LLPL	PE45429	$22.99	$21.84	$20.69	$19.77	50
PCB Mount		Solder	Surface Mount	PE44510	$29.79	$28.30	$26.81	$25.62	51
			Thru Hole	PE44512	$28.39	$26.97	$25.55	$24.42	52
	Female, Bulkhead Mount								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with .268 inch D Hole	PE44507	$31.59	$30.01	$28.43	$27.17	53
			RG316-DS, RG188-DS with .268 inch D Hole	PE44508	$24.59	$23.36	$22.13	$21.15	54
		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45685	$15.59	$14.81	$14.03	$13.41	55
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402 with .268 inch D Hole	PE44500	$28.79	$27.35	$25.91	$24.76	56
			PE-SR405AL, PE-SR405FL, RG405 with .268 inch D Hole	PE45218	$37.59	$35.71	$33.83	$32.33	57
	Female Right Angle								
PCB Mount		Solder	Surface Mount	PE44511	$18.99	$18.23	$17.66	$17.28	58

QN Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Crimp/Solder	LMR-240, PE-C240	PE45222	$39.59	$38.01	$36.82	$36.03	59
			RG213, RG215	PE44597	$90.99	$87.35	$84.62	$82.80	60
			RG55, RG141, RG142, RG223, RG400	PE44978	$37.59	$35.71	$33.83	$32.33	61
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195	PE45071	$33.39	$32.05	$31.05	$30.38	62
		Solder/Solder	PE-SR402AL, PE-SR402FL, RG402	PE44599	$46.39	$44.07	$41.75	$39.90	63

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

QN Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male Right Angle								
Cable Connectors		Crimp/Solder	LMR-400, PE-C400, LMR-400-DB	PE45223	$63.99	$60.79	$57.59	$55.03	64
			PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE44601	$54.99	$52.24	$49.49	$47.29	65
			RG214, RG225	PE44603	$55.99	$53.19	$50.39	$48.15	66
			RG55, RG141, RG142, RG223, RG400	PE44600	$57.99	$55.09	$52.19	$49.87	67
		Solder/Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44604	$53.99	$51.29	$48.59	$46.43	68
	Female, Bulkhead Mount								
Cable Connectors		Crimp/Solder	RG213, RG215 with .500 inch Diameter	PE44607	$60.99	$57.94	$54.89	$52.45	69
			RG214, RG225 with .500 inch Diameter	PE44608	$121.99	$117.11	$113.45	$111.01	70
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup	PE44610	$84.99	$80.74	$76.49	$73.09	71

SC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	See Web for Volume Pricing	ROW
	Male						
Cable Connectors		Clamp/Solder	RG213, RG214, RG8, RG9, RG225, RG393, RG215	PE4520	$223.99		72
			RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE45479	$157.99		73
		Crimp/Solder	RG214, RG9, RG225, RG393	PE4232	$78.99		74
			RG55, RG141, RG142, RG223, RG400	PE4231	$161.99		75
	Male Right Angle						
Cable Connectors		Clamp/Solder	RG213, RG214, RG8, RG9, RG225, RG393, RG215	PE4979	$215.99	See Web for Volume Pricing	76
			RG58, RG55, RG141, RG142, RG223, RG400	PE4978	$179.99		77
	Female, Bulkhead Mount						
Terminal		Solder	Eyelet with .655 inch D Hole	PE4980	$46.59		78

SHV Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4498	$49.79	$47.30	$44.81	$42.82	79
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4316	$35.39	$33.62	$31.85	$30.44	80
			RG59*, RG62*, RG71	PE4100	$32.39	$30.77	$29.15	$27.86	81
			RG8, RG213, RG214	PE4333	$50.99	$48.44	$45.89	$43.85	82
		Crimp/Solder	RG213, RG8	PE4496	$46.39	$44.07	$41.75	$39.90	83
			RG214, RG9, RG225, RG393	PE4349	$52.99	$50.34	$47.69	$45.57	84
			RG55, RG142, RG223, RG400	PE4497	$46.79	$44.45	$42.11	$40.24	85
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4194	$59.99	$56.99	$53.99	$51.59	86
			RG59*, RG62*, RG71	PE4343	$47.59	$45.21	$42.83	$40.93	87
	Plug, Bulkhead Mount								
Terminal		Solder	Solder Cup with .350 inch D Hole	PE44118	$62.99	$59.84	$56.69	$54.17	88

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

SHV Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Jack, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188 with .480 inch D Hole	PE45556	$64.99	$61.74	$58.49	$55.89	89
			RG213, RG214, RG8, RG9, RG225, RG393, RG215 with .480 inch D Hole	PE44049	$83.99	$79.79	$75.59	$72.23	90
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, LMR-400, PE-C195, PE-P195 with .480 inch D Hole	PE44080	$63.99	$60.79	$57.59	$55.03	91
			RG59*, RG62*, RG71 with .480 inch D Hole	PE4315	$63.99	$60.79	$57.59	$55.03	92
Terminal		Solder	Solder Cup with .350 inch D Hole	PE4239	$26.99	$25.64	$24.29	$23.21	93
			Solder Cup with .350 inch D Hole	PE4500	$83.99	$79.79	$75.59	$72.23	94
			Solder Cup with .480 inch D Hole	PE4499	$42.59	$40.46	$38.33	$36.63	95
	Jack, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .500 inch Hole Spacing	PE4501	$48.59	$46.16	$43.73	$41.79	96

SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	PE-P142LL	PE44826	$50.99	$48.44	$45.89	$43.85	97
			PE-P160LL	PE45440	$101.99	$96.89	$91.79	$87.71	98
			PE-P300LL	PE44808	$78.99	$75.04	$71.09	$67.93	99
			PE-P300LL	PE45042	$82.99	$82.99	$82.99	$82.99	1
			PE-SR401AL, PE-SR401FL, RG401	PE4403	$55.99	$53.19	$50.39	$48.15	2
			RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE4026	$38.19	$36.28	$34.37	$32.84	3
			RG178, RG196	PE4214	$69.99	$66.49	$62.99	$60.19	4
			RG180, RG195, PE-B150	PE4399	$31.39	$29.82	$28.25	$27.00	5
			RG188-DS, RG316-DS	PE4400	$40.79	$38.75	$36.71	$35.08	6
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4332	$113.99	$108.29	$102.59	$98.03	7
			RG316, RG174, LMR-100	PE45142	$19.79	$18.80	$17.81	$17.02	8
			RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE4027	$36.99	$35.14	$33.29	$31.81	9
			RG58, RG303, LMR-195, PE-P195	PE45140	$30.99	$29.44	$27.89	$26.65	10
		Crimp/Crimp	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4003	$14.79	$14.05	$13.31	$12.72	11
		Crimp/ Non-Solder Contact	LMR-240, PE-C240	EZ-240-SM-X	$10.39	$10.39	$10.39	$10.39	12
		Crimp/Solder	LMR-195, PE-C195	TC-195-SM-SS-X	$15.59	$15.59	$15.59	$15.59	13
			LMR-200, PE-C200	PE45040	$10.19	$9.78	$9.48	$9.27	14
			LMR-200, PE-C200	TC-200-SM-SS-X	$14.79	$14.79	$14.79	$14.79	15
			LMR-240, PE-C240, LMR-240-UF	TC-240-SM-SS-X	$10.99	$10.99	$10.99	$10.99	16
			LMR-400, PE-C400	TC-400-SM-X	$19.19	$19.19	Call	Call	17
			PE-B150, RG180, RG195	PE4578	$32.79	$31.15	$29.51	$28.20	18
			PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE44460	$98.99	$95.03	$92.06	$90.08	19
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44637	$23.59	$22.41	$21.23	$20.29	20
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44668	$37.59	$35.71	$33.83	$32.33	21
			PE-P195	PE44203	$23.59	$22.41	$21.23	$20.29	22
			RG142, RG223, RG400, RG55	PE44461	$79.99	$76.79	$74.39	$72.79	23
			RG174, RG316, RG188	PE45145	$15.79	$15.00	$14.21	$13.58	24
			RG178, RG196	PE4398	$26.99	$25.64	$24.29	$23.21	25
			RG188-DS, RG316-DS	PE4401	$8.39	$7.97	$7.55	$7.22	26
			RG55, RG142, RG223, RG400, RG141	PE4008	$17.19	$16.33	$15.47	$14.78	27
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4215	$16.59	$15.76	$14.93	$14.27	28
			RG59*, RG62*, RG71	PE4294	$34.19	$32.48	$30.77	$29.40	29

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Crimp/Solder (Captive Contact)	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4589	$24.99	$23.74	$22.49	$21.49	30
			RG55, RG141, RG142, RG223, RG400	PE4576	$37.79	$35.90	$34.01	$32.50	31
			RG58	PE4577	$31.99	$30.39	$28.79	$27.51	32
		Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44691	$11.99	$11.39	$10.79	$10.31	33
			RG405, RG405 Tinned	PE45481	$50.99	$48.44	$45.89	$43.85	34
			RG405, RG405 Tinned, PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN	PE45480	$50.99	$48.44	$45.89	$43.85	35
		Solder (Without Contact)	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE4007	$15.79	$15.00	$14.21	$13.58	36
		Solder/Solder	PE-020SR	PE4918	$60.99	$57.94	$54.89	$52.45	37
			PE-034SR	PE4917	$103.99	$98.79	$93.59	$89.43	38
			PE-047SR, PE-SR047AL, PE-SR047FL	PE4404	$38.59	$36.66	$34.73	$33.19	39
			PE-047SR, PE-SR047AL, PE-SR047FL	PE44757	$46.99	$43.70	$40.41	$37.59	40
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45678	$9.29	$8.83	$8.36	$7.99	41
			PE-SR401AL, PE-SR401FL, RG401	PE4907	$57.99	$55.09	$52.19	$49.87	42
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE4112	$14.79	$14.05	$13.31	$12.72	43
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44690	$13.59	$12.91	$12.23	$11.69	44
			PE-SR405AL, PE-SR405FL, RG405	PE4005	$9.99	$9.49	$8.99	$8.59	45
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4036	$19.99	$18.99	$17.99	$17.19	46
			RG178, RG196	PE4213	$24.99	$23.74	$22.49	$21.49	47
			RG188-DS, RG316-DS	PE4402	$22.59	$21.46	$20.33	$19.43	48
			RG405, PE-SR405FL, PE-SR405FLJ	PE45135	$12.59	$11.96	$11.33	$10.83	49
			RG58, RG55, RG142, RG223, RG400	PE4037	$20.79	$19.75	$18.71	$17.88	50
			SPP-250-LLPL	PE45543	$18.99	$18.04	$17.09	$16.33	51
			TFT-402, TFT-402-LF	TC-402-SM-LP	$8.89	$8.89	$8.89	$8.89	52
		Solder/Solder (Captive Contact)	RG174, RG316, RG188	PE4590	$22.99	$21.84	$20.69	$19.77	53
			RG58, RG55, RG142, RG223, RG400	PE4587	$28.99	$27.83	$26.96	$26.38	54
PCB Mount		Clamp	Vertical Launch	PE45460	$46.59	$44.26	$41.93	$40.07	55
			Vertical Launch	PE45461	$49.39	$47.41	$45.93	$44.94	56
		Solder	.042 inch End Launch	PE44209	$38.19	$35.52	$32.84	$30.55	57
			.042 inch End Launch	PE44210	$42.79	$40.65	$38.51	$36.80	58
			.062 inch End Launch	PE4912	$40.39	$38.37	$36.35	$34.74	59
			.062 inch End Launch	PE4913	$41.99	$39.89	$37.79	$36.11	60
			Thru Hole with .200 inch x .067 inch Hole Spacing	PE4525	$28.39	$26.97	$25.55	$24.42	61
	Male, Bulkhead Mount								
Terminal		Solder	Solder Cup with .235 inch D Hole	PE4354	$26.19	$24.88	$23.57	$22.52	62
			Stub with .250 inch Diameter	PE4531	$69.99	$66.49	$62.99	$60.19	63
	Male, 2 Hole Flange Mount								
Field Replaceable		Field Replaceable	.036 inch Pin	PE44032	$23.79	$22.60	$21.41	$20.46	64
Terminal		Solder	Solder Cup	PE45139	$13.39	$12.72	$12.05	$11.52	65
			Solder Cup with .481 inch Hole Spacing	PE4125	$38.39	$36.47	$34.55	$33.02	66
			Stub with .481 inch Hole Spacing	PE4127	$19.19	$18.23	$17.27	$16.50	67
	Male, 4 Hole Flange Mount								
Field Replaceable		Field Replaceable	.012 inch Pin	PE44005	$45.79	$43.50	$41.21	$39.38	68
			.012 inch Pin	PE44018	$33.99	$32.29	$30.59	$29.23	69
			.015 inch Pin	PE44019	$56.99	$54.14	$51.29	$49.01	70
			.018 inch Pin	PE44007	$29.39	$27.92	$26.45	$25.28	71
			.020 inch Pin	PE44008	$48.59	$46.16	$43.73	$41.79	72
			.020 inch Pin	PE44021	$30.39	$28.87	$27.35	$26.14	73
			.036 inch Pin	PE44009	$29.79	$28.30	$26.81	$25.62	74

Connectors

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	PRICE See Web for Volume Pricing	ROW
	Male, 4 Hole Flange Mount						
Terminal		Solder	Pin with .340 inch Hole Spacing	PE4541	$68.99		75
			Solder Cup with .340 inch Hole Spacing	PE45204	$64.99		76
			Stub with .340 inch Hole Spacing	PE4126	$37.79		77
	Male Right Angle						
Cable Connectors		Clamp/Solder	PE-P142LL	PE44817	$157.99	See Web for Volume Pricing	78
			PE-P160LL	PE45442	$141.99		79
			PE-P300LL	PE45041	$159.99		80
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44996	$125.99		81
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE4028	$44.79		82
			RG178, RG196	PE4108	$28.19		83
			RG180, RG195	PE4579	$33.39		84
			RG188-DS, RG316-DS	PE4407	$67.99		85
			RG58, RG55, RG142, RG223, RG303, RG400, LMR-195, PE-C195	PE45048	$64.99		86
		Crimp/ Non-Solder Contact	LMR-240	EZ-240-SM-RA-X	$14.39		87
		Crimp/Solder	PE-B150, RG180, RG195	PE4580	$32.39		88
			PE-C200, LMR-200	PE45546	$30.59		89
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44638	$39.99		90
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4009	$27.19		91
			RG178, RG196	PE4296	$36.59		92
			RG188-DS, RG316-DS	PE4408	$23.39		93
			RG316, RG174, RG188	PE45144	$26.59		94
			RG55, RG142, RG223, RG400, RG141	PE4002	$24.39		95
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4405	$16.39		96
			RG59*, RG62*, RG71	PE4327	$47.39		97
		Solder/Solder	PE-020SR	PE4920	$86.99		98
			PE-034SR	PE4919	$77.99		99
			PE-047SR, PE-SR047AL, PE-SR047FL	PE45282	$78.99		1
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45679	$10.79		2
			PE-SR401AL, PE-SR401FL, RG401	PE4932	$78.99		3
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE4083	$27.99		4
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44693	$18.79		5
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44692	$16.39		6
			PE-SR405AL, PE-SR405FL, RG405	PE4025	$38.79		7
			RG178, RG196	PE4406	$32.39		8
			RG188-DS, RG316-DS	PE4409	$32.39		9
			RG316, RG174, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4038	$26.99		10
			RG58, RG55, RG142, RG223, RG400	PE4039	$24.39		11
			SPP-250-LLPL	PE45434	$20.19		12
			TFT-402, TFT-402-LF	TC-402-SM-RA-LP	$14.79		13
	Female						
Cable Connectors		Clamp/Solder	PE-P142LL	PE44814	$88.99		14
			RG178, RG196	PE4591	$38.39		15
			RG188-DS, RG316-DS	PE4415	$42.99		16
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393	PE4411	$81.99		17
			RG316, RG174, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE4030	$43.59		18
			RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE4031	$58.99		19
		Crimp/Solder	PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44639	$32.39		20
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44669	$62.99		21
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE4414	$24.19		22
			RG178, RG196	PE4325	$40.79		23

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female								
Cable Connectors		Crimp/Solder	RG188-DS, RG316-DS	PE4416	$26.59	$25.26	$23.93	$22.87	24
			RG316, RG174, LMR-100, RG188, PE-B100, PE-C100, 0.100 inch	PE45137	$11.19	$10.63	$10.07	$9.62	25
			RG55, RG142, RG223	PE4412	$20.99	$19.94	$18.89	$18.05	26
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195	PE4413	$23.79	$22.60	$21.41	$20.46	27
			RG59*, RG62*	PE4326	$36.99	$35.14	$33.29	$31.81	28
		Solder/Solder	PE-020SR	PE4922	$84.99	$80.74	$76.49	$73.09	29
			PE-034SR	PE4921	$77.99	$74.09	$70.19	$67.07	30
			PE-047SR, PE-SR047AL, PE-SR047FL	PE4418	$45.99	$43.69	$41.39	$39.55	31
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45680	$9.88	$9.39	$8.89	$8.50	32
			PE-SR401AL, PE-SR401FL, RG401	PE4930	$40.59	$38.56	$36.53	$34.91	33
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE4115	$23.79	$22.60	$21.41	$20.46	34
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44695	$16.39	$15.57	$14.75	$14.10	35
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44694	$11.79	$11.20	$10.61	$10.14	36
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405	PE4116	$30.79	$29.25	$27.71	$26.48	37
			RG178, RG196	PE4592	$33.79	$32.10	$30.41	$29.06	38
			RG188-DS, RG316-DS	PE4417	$20.39	$19.37	$18.35	$17.54	39
			RG316, RG174, RG188	PE4040	$21.19	$20.13	$19.07	$18.22	40
			RG58, RG55, RG142, RG223, RG400	PE4041	$22.79	$21.65	$20.51	$19.60	41
			SPP-250-LLPL	PE45432	$19.99	$18.99	$17.99	$17.19	42
PCB Mount		Clamp	Vertical Launch	PE45458	$46.19	$43.88	$41.57	$39.72	43
			Vertical Launch	PE45459	$46.19	$43.88	$41.57	$39.72	44
		Clamp/Solder (Captive Contact)	End Launch	PE45462	$64.99	$61.74	$58.49	$55.89	45
			End Launch	PE45463	$64.99	$61.74	$58.49	$55.89	46
			End Launch	PE45464	$64.99	$61.74	$58.49	$55.89	47
			End Launch	PE45465	$64.99	$61.74	$58.49	$55.89	48
			End Launch	PE45466	$62.99	$59.84	$56.69	$54.17	49
		Solder	.031 inch End Launch	PE44206	$26.59	$25.26	$23.93	$22.87	50
			.042 inch End Launch	PE44204	$32.19	$30.58	$28.97	$27.68	51
			.042 inch End Launch	PE44207	$34.19	$32.48	$30.77	$29.40	52
			.047 inch End Launch	PE44205	$36.79	$34.95	$33.11	$31.64	53
			.047 inch End Launch	PE44208	$34.99	$33.24	$31.49	$30.09	54
			.062 inch End Launch	PE4542	$24.39	$23.17	$21.95	$20.98	55
			.062 inch End Launch	PE4543	$35.99	$34.19	$32.39	$30.95	56
			.078 inch End Launch	PE44614	$43.79	$41.60	$39.41	$37.66	57
			End Launch	PE44235	$29.79	$28.30	$26.81	$25.62	58
			Surface Mount	PE4910	$23.79	$22.60	$21.41	$20.46	59
			Thru Hole	PE4117	$19.19	$18.23	$17.27	$16.50	60
			Thru Hole with .200 inch x .067 inch Hole Spacing	PE44827	$14.39	$13.67	$12.95	$12.38	61
		Solder/Solder (Captive Contact)	1/16 inch Stripline	PE4534	$55.99	$53.19	$50.39	$48.15	62
			1/8 inch Stripline	PE4190	$55.99	$53.19	$50.39	$48.15	63
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	PE-P160LL	PE45441	$119.99	$113.99	$107.99	$103.19	64
			RG178, RG196 with .235 inch D Hole	PE4421	$50.99	$48.44	$45.89	$43.85	65
			RG188-DS, RG316-DS with .235 inch D Hole	PE4424	$53.99	$51.29	$48.59	$46.43	66
			RG316, RG174, RG188, PE-B100, PE-C100, .100 inch, LMR-100 with .235 inch D Hole	PE4032	$48.19	$45.78	$43.37	$41.44	67
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, LMR-400, PE-C195, PE-P195 with .235 inch D Hole	PE4033	$51.99	$49.39	$46.79	$44.71	68
		Crimp/Solder	RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with .235 inch D Hole	PE44643	$27.19	$25.83	$24.47	$23.38	69
			RG178, RG196 with .235 inch D Hole	PE4422	$38.19	$36.28	$34.37	$32.84	70
			RG178, RG196 with .235 inch D Hole	PE45292	$23.39	$22.22	$21.05	$20.12	71
			RG188-DS, RG316-DS with .235 inch D Hole	PE4425	$30.19	$28.68	$27.17	$25.96	72
			RG316, RG174, LMR-100	PE45136	$22.99	$21.84	$20.69	$19.77	73
			RG316, RG174, RG188, PE-B100, PE-C100, .100 inch, LMR-100 with .235 inch D Hole	PE4427	$23.79	$22.60	$21.41	$20.46	74
			RG55, RG142, RG223, RG141 with .235 inch D Hole	PE4419	$25.99	$24.69	$23.39	$22.35	75

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
Female, Bulkhead Mount									
Cable Connectors		Crimp/Solder	RG58 with .235 inch D Hole	PE4420	$25.79	$24.50	$23.21	$22.18	76
			RG58, RG303, LMR-195	PE45138	$15.19	$14.43	$13.67	$13.06	77
			RG58, RG303, LMR-195, PE-P195	PE45141	$16.99	$16.14	$15.29	$14.61	78
			RG59*, RG62*, RG71 with .235 inch D Hole	PE4914	$34.39	$32.67	$30.95	$29.58	79
		Solder/Solder	PE-020SR with .235 inch D Hole	PE4924	$85.99	$81.69	$77.39	$73.95	80
			PE-034SR with .235 inch D Hole	PE4923	$88.99	$84.54	$80.09	$76.53	81
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45681	$13.19	$12.53	$11.87	$11.34	82
			PE-SR401AL, PE-SR401FL, RG401 with .235 inch D Hole	PE4931	$76.99	$73.14	$69.29	$66.21	83
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44697	$15.19	$14.43	$13.67	$13.06	84
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402 with .235 inch D Hole	PE45554	$22.39	$21.27	$20.15	$19.26	85
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405 with .235 inch D Hole	PE44696	$16.79	$15.95	$15.11	$14.44	86
			PE-SR405AL, PE-SR405FL, RG405 with .235 inch D Hole	PE4119	$21.79	$20.70	$19.61	$18.74	87
			RG178, RG196 with .235 inch D Hole	PE4423	$32.79	$31.15	$29.51	$28.20	88
			RG188-DS, RG316-DS with .235 inch D Hole	PE4426	$27.59	$26.21	$24.83	$23.73	89
			RG316, RG174, RG188 with .235 inch D Hole	PE4188	$23.99	$22.79	$21.59	$20.63	90
			RG58, RG55, RG142, RG223 with .235 inch D Hole	PE4353	$25.59	$24.31	$23.03	$22.01	91
PCB Mount		Solder	.042 inch End Launch with .250 inch Diameter	PE44211	$34.79	$33.05	$31.31	$29.92	92
			.042 inch End Launch with .250 inch Diameter	PE44213	$31.79	$30.20	$28.61	$27.34	93
			.062 inch End Launch with .250 inch Diameter	PE44212	$31.59	$30.01	$28.43	$27.17	94
			.062 inch End Launch with .250 inch Diameter	PE44214	$33.59	$31.91	$30.23	$28.89	95
			End Launch	PE45134	$32.99	$31.34	$29.69	$28.37	96
			Thru Hole with .235 inch D Hole	PE4524	$23.59	$22.41	$21.23	$20.29	97
Terminal			Pin	PE45547	$21.19	$20.13	$19.07	$18.22	98
			Solder Cup with .235 inch D Hole	PE4101	$25.39	$24.12	$22.85	$21.84	99
			Solder Cup with .235 inch D Hole	PE4529	$63.99	$60.79	$57.59	$55.03	1
			Solder Cup with .250 inch Diameter	PE4549	$37.99	$36.09	$34.19	$32.67	2
			Solder Cup with .350 inch D Hole	PE4536	$58.99	$56.04	$53.09	$50.73	3
			Stub with .235 inch D Hole	PE4528	$57.99	$55.09	$52.19	$49.87	4
			Stub with .250 inch Diameter	PE4189	$21.79	$20.70	$19.61	$18.74	5
			Stub with .250 inch Diameter	PE44591	$38.59	$36.66	$34.73	$33.19	6
			Stub with .250 inch Diameter	PE4530	$40.39	$38.37	$36.35	$34.74	7
			Stub with .250 inch Diameter	PE4532	$36.79	$34.95	$33.11	$31.64	8
Female, 2 Hole Flange Mount									
Cable Connectors		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL with .481 inch Hole Spacing	PE4547	$36.19	$34.38	$32.57	$31.12	9
			PE-SR402AL, PE-SR402FL, RG402 with .481 inch Hole Spacing	PE4196	$39.39	$37.42	$35.45	$33.88	10
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405 with .481 inch Hole Spacing	PE4197	$32.59	$30.96	$29.33	$28.03	11
Field Replaceable		Field Replaceable	.012 inch Pin	PE45217	$36.79	$34.95	$33.11	$31.64	12
			.015 inch Pin	PE44024	$41.19	$39.13	$37.07	$35.42	13
			.036 inch Pin	PE45055	$35.99	$34.19	$32.39	$30.95	14
			0.009 inch Pin	PE45572	$36.39	$34.57	$32.75	$31.30	15
			0.009 inch Pin	PE45578	$31.59	$30.01	$28.43	$27.17	16
			0.009 inch Pin with .481 inch Hole Spacing	PE45584	$30.19	$28.68	$27.17	$25.96	17
			0.012 inch Pin	PE45573	$29.79	$28.30	$26.81	$25.62	18
			0.012 inch Pin	PE45579	$25.19	$23.93	$22.67	$21.66	19
			0.012 inch Pin with .481 inch Hole Spacing	PE45585	$27.19	$25.83	$24.47	$23.38	20
			0.015 inch Pin	PE45574	$34.79	$33.05	$31.31	$29.92	21
			0.015 inch Pin	PE45580	$27.99	$26.59	$25.19	$24.07	22
			0.015 inch Pin with .481 inch Hole Spacing	PE45586	$23.39	$22.22	$21.05	$20.12	23
			0.018 inch Pin	PE45575	$31.99	$30.39	$28.79	$27.51	24
			0.018 inch Pin	PE45581	$27.79	$26.40	$25.01	$23.90	25
			0.018 inch Pin with .481 inch Hole Spacing	PE45587	$25.19	$23.93	$22.67	$21.66	26
			0.02 inch Pin	PE45576	$28.59	$27.16	$25.73	$24.59	27
			0.02 inch Pin	PE45582	$27.79	$26.40	$25.01	$23.90	28
			0.02 inch Pin with .481 inch Hole Spacing	PE45588	$25.59	$24.31	$23.03	$22.01	29
			0.036 inch Pin	PE45577	$28.79	$27.35	$25.91	$24.76	30
			0.036 inch Pin	PE45583	$31.79	$30.20	$28.61	$27.34	31
			0.036 inch Pin with .481 inch Hole Spacing	PE45589	$24.19	$22.98	$21.77	$20.80	32

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, 2 Hole Flange Mount								
Terminal		Compression	Stub with .481 inch Hole Spacing	PE44340	$78.99	$75.04	$71.09	$67.93	33
		Solder	Solder Cup with .481 inch Hole Spacing	PE4004	$23.19	$22.03	$20.87	$19.94	34
			Solder Cup with .481 inch Hole Spacing	PE44341	$76.99	$73.14	$69.29	$66.21	35
			Stub	PE45039	$19.39	$18.61	$18.03	$17.64	36
			Stub	PE45067	$18.79	$17.85	$16.91	$16.16	37
			Stub with .481 inch Hole Spacing	PE4128	$24.99	$23.74	$22.49	$21.49	38
			Stub with .481 inch Hole Spacing	PE4128-SF	$23.79	$22.60	$21.41	$20.46	39
			Tab with .481 inch Hole Spacing	PE4370	$31.59	$30.01	$28.43	$27.17	40
	Female, 4 Hole Flange Mount								
Cable Connectors		Clamp/Solder	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100A-FR, PE-C100, PE-B100 with .340 inch Hole Spacing	PE4034	$85.99	$81.69	$77.39	$73.95	41
			RG58, RG55, RG141, RG142, RG223, RG400 with .340 inch Hole Spacing	PE4035	$76.99	$73.14	$69.29	$66.21	42
		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL with .340 inch Hole Spacing	PE4548	$103.99	$98.79	$93.59	$89.43	43
			RG402, RG402 Tinned, PE-SR402FL, PE-SR402AL, PE-SR402FLJ, PE-SR402TN with .340 inch Hole Spacing	PE4121	$49.19	$46.73	$44.27	$42.30	44
			RG405, RG405 Tinned, PE-SR405FL, PE-SR405AL, PE-SR405FLJ, PE-SR405TN	PE44998	$40.99	$38.94	$36.89	$35.25	45
Field Replaceable		Field Replaceable	.012 inch Pin	PE44000	$47.39	$45.02	$42.65	$40.76	46
			.012 inch Pin	PE44010	$45.39	$43.12	$40.85	$39.04	47
			.015 inch Pin	PE44001	$43.99	$41.79	$39.59	$37.83	48
			.015 inch Pin	PE45216	$29.59	$28.11	$26.63	$25.45	49
			.020 inch Pin	PE44003	$44.39	$42.17	$39.95	$38.18	50
			.020 inch Pin	PE45215	$26.39	$25.07	$23.75	$22.70	51
			.036 inch Pin	PE44004	$47.39	$45.02	$42.65	$40.76	52
			.036 inch Pin	PE45053	$42.59	$40.46	$38.33	$36.63	53
			0.009 inch Pin	PE45560	$40.59	$38.56	$36.53	$34.91	54
			0.009 inch Pin	PE45566	$43.39	$41.22	$39.05	$37.32	55
			0.012 inch Pin	PE45561	$32.39	$30.77	$29.15	$27.86	56
			0.012 inch Pin	PE45567	$34.79	$33.05	$31.31	$29.92	57
			0.015 inch Pin	PE45562	$33.19	$31.53	$29.87	$28.54	58
			0.015 inch Pin	PE45568	$35.79	$34.00	$32.21	$30.78	59
			0.018 inch Pin	PE45563	$35.79	$34.00	$32.21	$30.78	60
			0.018 inch Pin	PE45569	$37.59	$35.71	$33.83	$32.33	61
			0.02 inch Pin	PE45564	$41.79	$39.70	$37.61	$35.94	62
			0.02 inch Pin	PE45570	$38.19	$36.28	$34.37	$32.84	63
			0.036 inch Pin	PE45565	$37.39	$35.52	$33.65	$32.16	64
			0.036 inch Pin	PE45571	$37.79	$35.90	$34.01	$32.50	65
Terminal		Solder	Pin with .340 inch Hole Spacing	PE4217	$33.59	$31.91	$30.23	$28.89	66
			Pin with .340 inch Hole Spacing	PE4540	$63.99	$60.79	$57.59	$55.03	67
			Pin with .375 inch x .500 inch Hole Spacing	PE4538	$53.99	$51.29	$48.59	$46.43	68
			Solder Cup with .340 inch Hole Spacing	PE4000	$29.59	$28.11	$26.63	$25.45	69
			Solder Cup with .340 inch Hole Spacing	PE4537	$41.39	$39.32	$37.25	$35.60	70
			Solder Cup with .500 inch Hole Spacing	PE4527	$35.39	$33.62	$31.85	$30.44	71
			Solder Cup with .718 inch Hole Spacing	PE4218	$36.59	$34.76	$32.93	$31.47	72
			Stub	PE4111	$53.99	$51.29	$48.59	$46.43	73
			Stub with .340 inch Hole Spacing	PE4099	$23.19	$22.03	$20.87	$19.94	74
			Stub with .500 inch Hole Spacing	PE4533	$33.79	$32.10	$30.41	$29.06	75
			Tab with .340 inch Hole Spacing	PE4186	$27.79	$26.40	$25.01	$23.90	76
			Tab with .375 inch x .500 inch Hole Spacing	PE4539	$41.39	$39.32	$37.25	$35.60	77
	Female, Press-In								
Terminal		Solder	Tab with .200 inch Diameter	PE44240	$36.99	$35.14	$33.29	$31.81	78
			Tab with .200 inch Diameter	PE44241	$41.39	$39.32	$37.25	$35.60	79
	Female Right Angle								
PCB Mount		Solder	Surface Mount	PE4911	$35.79	$34.00	$32.21	$30.78	80
			Thru Hole	PE45698	$27.59	$26.21	$24.83	$23.73	81

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female Right Angle, Bulkhead Mount								
PCB Mount		Solder	Thru Hole with .235 inch D Hole	PE4545	$38.19	$36.28	$34.37	$32.84	82
Terminal			Solder Cup with .235 inch D Hole	PE4300	$68.99	$65.54	$62.09	$59.33	83
	Female Right Angle, 2 Hole Flange Mount								
Terminal		Solder	Pin with .481 inch Hole Spacing	PE44237	$68.99	$65.54	$62.09	$59.33	84
			Pin with .481 inch Hole Spacing	PE44238	$63.99	$60.79	$57.59	$55.03	85
			Pin with .481 inch Hole Spacing	PE44239	$65.99	$62.69	$59.39	$56.75	86
			Pin with .481 inch Hole Spacing	PE44593	$64.99	$61.74	$58.49	$55.89	87
	Female Right Angle, 4 Hole Flange Mount								
Field Replaceable		Field Replaceable	.012 inch Pin	PE44015	$68.17	$64.76	$61.35	$58.63	88
Terminal		Solder	Pin with .340 inch Hole Spacing	PE44236	$40.19	$38.18	$36.17	$34.56	89
			Solder Cup with .340 inch Hole Spacing	PE4123	$49.19	$46.73	$44.27	$42.30	90

Reverse Polarity SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE4770	$48.39	$45.97	$43.55	$41.62	91
			RG178, RG196	PE4773	$17.19	$16.33	$15.47	$14.78	92
			RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE4766	$44.19	$41.98	$39.77	$38.00	93
		Crimp/Solder	PE-B150, RG180, RG195	PE4777	$20.19	$19.18	$18.17	$17.36	94
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44664	$32.99	$31.34	$29.69	$28.37	95
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44666	$44.59	$42.36	$40.13	$38.35	96
			RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE4771	$27.39	$26.02	$24.65	$23.56	97
			RG178B/U, RG196A/U	PE45008	$55.99	$53.19	$50.39	$48.15	98
			RG188-DS, RG316-DS	PE45183	$24.99	$23.74	$22.49	$21.49	99
			RG55, RG141, RG142, RG223, RG400	PE4767	$28.79	$27.35	$25.91	$24.76	1
			RG58	PE4769	$29.39	$27.92	$26.45	$25.28	2
		Solder/Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44724	$27.99	$26.59	$25.19	$24.07	3
			RG174, RG316, RG188	PE4772	$27.19	$25.83	$24.47	$23.38	4
			RG178, RG196	PE4775	$33.79	$32.44	$31.42	$30.75	5
			RG58, RG55, RG141, RG142, RG223, RG400	PE4768	$29.39	$27.92	$26.45	$25.28	6
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188	PE4784	$73.99	$70.29	$66.59	$63.63	7
			RG58, RG55, RG141, RG142, RG223, RG400	PE4780	$53.99	$51.29	$48.59	$46.43	8
		Crimp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE4785	$73.99	$70.29	$66.59	$63.63	9
			RG178, RG196	PE4788	$49.39	$46.92	$44.45	$42.48	10
			RG188-DS, RG316-DS	PE45185	$56.99	$54.14	$51.29	$49.01	11
			RG55, RG142, RG223, RG400	PE44975	$51.99	$49.39	$46.79	$44.71	12
			RG58, RG141, PE-C195, PE-P195	PE45012	$44.59	$42.36	$40.13	$38.35	13
		Solder/Solder	PE-SR402AL, PE-SR402FL, RG402	PE4790	$59.99	$56.99	$53.99	$51.59	14
			RG174, RG316, RG188	PE4786	$49.79	$47.30	$44.81	$42.82	15
			RG58, RG55, RG141, RG142, RG223, RG400	PE4782	$49.79	$47.30	$44.81	$42.82	16
	Female								
Cable Connectors		Clamp/Solder	RG178, RG196	PE4850	$16.19	$15.54	$15.06	$14.73	17
			RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE4792	$42.79	$40.65	$38.51	$36.80	18

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

Reverse Polarity SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female								
Cable Connectors		Crimp/Crimp	LMR-400, PE-C400, PE-B400, PE-B405	PE45397	$8.19	$7.78	$7.37	$7.04	19
		Crimp/Solder	PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44665	$35.19	$33.43	$31.67	$30.26	20
			RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100, RG179	PE4797	$40.79	$38.75	$36.71	$35.08	21
			RG178, RG196	PE4799	$39.79	$37.80	$35.81	$34.22	22
			RG188-DS, RG316-DS	PE45186	$36.79	$34.95	$33.11	$31.64	23
			RG55, RG141, RG142, RG223, RG400	PE4793	$43.79	$41.60	$39.41	$37.66	24
			RG58	PE4795	$34.59	$32.86	$31.13	$29.75	25
		Solder/Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44723	$34.39	$32.67	$30.95	$29.58	26
			PE-SR402AL, PE-SR402FL, RG402	PE4852	$40.59	$38.56	$36.53	$34.91	27
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE4853	$22.59	$21.46	$20.33	$19.43	28
			RG174, RG316, RG188	PE4798	$35.19	$33.43	$31.67	$30.26	29
			RG178, RG196	PE4851	$30.79	$29.25	$27.71	$26.48	30
			RG58, RG55, RG141, RG142, RG223, RG400	PE4794	$32.79	$31.15	$29.51	$28.20	31
PCB Mount		Solder	.062 inch End Launch	PE4874	$35.79	$34.00	$32.21	$30.78	32
			Thru Hole with .200 inch x .067 inch Hole Spacing	PE4869	$31.19	$29.63	$28.07	$26.82	33
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188 with .235 inch D Hole	PE4858	$54.99	$52.24	$49.49	$47.29	34
			RG178, RG196 with .235 inch D Hole	PE4861	$49.39	$46.92	$44.45	$42.48	35
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, LMR-195, PE-C195, PE-P195 with .235 inch D Hole	PE4854	$49.39	$46.92	$44.45	$42.48	36
		Crimp/Solder	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100A-FR, PE-C100, PE-B100 with .235 inch D Hole	PE4859	$37.19	$35.33	$33.47	$31.98	37
			RG178, RG196 with .235 inch D Hole	PE4862	$32.99	$31.34	$29.69	$28.37	38
			RG188-DS, RG316-DS with .235 inch D Hole	PE45189	$34.99	$33.24	$31.49	$30.09	39
			RG196, RG178	PE45004	$23.79	$22.84	$22.12	$21.65	40
			RG55, RG141, RG142, RG223, RG400 with .235 inch D Hole	PE4855	$38.39	$36.47	$34.55	$33.02	41
			RG58 with .235 inch D Hole	PE4857	$31.59	$30.01	$28.43	$27.17	42
		Solder/Solder	PE-SR402AL, PE-SR402FL, RG402 with .235 inch D Hole	PE4864	$46.59	$44.26	$41.93	$40.07	43
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405 with .235 inch D Hole	PE4865	$52.99	$50.34	$47.69	$45.57	44
			RG174, RG316, RG188 with .235 inch D Hole	PE4860	$32.79	$31.15	$29.51	$28.20	45
			RG178, RG196 with .235 inch D Hole	PE4863	$32.39	$30.77	$29.15	$27.86	46
			RG58, RG55, RG141, RG142, RG223, RG400 with .235 inch D Hole	PE4856	$32.99	$31.34	$29.69	$28.37	47
PCB Mount		Solder	Thru Hole with .250 inch Diameter	PE4872	$31.39	$29.82	$28.25	$27.00	48
Terminal			Solder Cup with .235 inch D Hole	PE4868	$31.99	$30.39	$28.79	$27.51	49
			Solder Cup with .235 inch D Hole	PE4871	$31.79	$30.20	$28.61	$27.34	50
	Female, 2 Hole Flange Mount								
Terminal		Solder	Solder Cup with .481 inch Hole Spacing	PE4867	$37.59	$35.71	$33.83	$32.33	51
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .340 inch Hole Spacing	PE4866	$26.79	$25.45	$24.11	$23.04	52
	Female Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4870	$46.19	$43.88	$41.57	$39.72	53

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

Reverse Polarity SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female Right Angle, Bulkhead Mount								
PCB Mount		Solder	Thru Hole with .250 inch Diameter	PE4875	$64.99	$61.74	$58.49	$55.89	54

Reverse Thread SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE44184	$17.99	$17.27	$16.73	$16.37	55
			RG178, RG196	PE44185	$32.79	$31.15	$29.51	$28.20	56
			RG188-DS, RG316-DS	PE45165	$28.79	$27.35	$25.91	$24.76	57
			RG55, RG141, RG142, RG223, RG400	PE44182	$34.59	$32.86	$31.13	$29.75	58
			RG58	PE44183	$29.99	$28.49	$26.99	$25.79	59
	Male Right Angle								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188	PE44188	$61.99	$58.89	$55.79	$53.31	60
			RG178, RG196	PE44189	$61.99	$58.89	$55.79	$53.31	61
			RG55, RG141, RG142, RG223, RG400	PE44186	$57.99	$55.09	$52.19	$49.87	62
			RG58	PE44187	$48.79	$46.35	$43.91	$41.96	63
	Female								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188	PE44192	$36.39	$34.57	$32.75	$31.30	64
			RG178, RG196	PE44193	$41.59	$39.51	$37.43	$35.77	65
			RG55, RG141, RG142, RG223, RG400	PE44190	$40.79	$38.75	$36.71	$35.08	66
			RG58	PE44191	$33.59	$31.91	$30.23	$28.89	67
PCB Mount		Solder	.062 inch End Launch	PE44201	$39.19	$37.23	$35.27	$33.70	68
			.062 inch End Launch	PE44202	$39.19	$37.23	$35.27	$33.70	69
			Thru Hole with .200 inch x .067 inch Hole Spacing	PE44198	$39.19	$37.23	$35.27	$33.70	70
	Female, Bulkhead Mount								
Cable Connectors		Crimp/Solder	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100A-FR, PE-C100, PE-B100 with .235 inch D Hole	PE44196	$33.79	$32.10	$30.41	$29.06	71
			RG178, RG196 with .235 inch D Hole	PE44197	$41.19	$39.13	$37.07	$35.42	72
			RG55, RG141, RG142, RG223, RG400 with .235 inch D Hole	PE44194	$38.79	$36.85	$34.91	$33.36	73
			RG58 with .235 inch D Hole	PE44195	$34.79	$33.05	$31.31	$29.92	74
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .340 inch Hole Spacing	PE44200	$44.79	$42.55	$40.31	$38.52	75
	Female Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE44199	$43.99	$41.79	$39.59	$37.83	76

SMA, 2.92mm Torque Wrenches



Type	Bit Hex Size (in.)	Preset Torque (in.-lbs.)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
SMA, 2.92mm	5/16 inch	5 in-lbs	PE5019-19	$223.35	See Web for Volume Pricing	
		8 in-lbs	PE5011-1	$291.99		

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

SMB Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Clamp/Solder	PE-SR405AL, PE-SR405FL, RG405	PE4356	$22.99	$22.07	$21.38	$20.92	77
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE4200	$22.59	$21.46	$20.33	$19.43	78
			RG178, RG196	PE4250	$28.99	$27.54	$26.09	$24.93	79
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4046	$17.39	$16.52	$15.65	$14.96	80
			RG178, RG196	PE4080	$21.19	$20.13	$19.07	$18.22	81
			RG316-DS, RG188-DS	PE44792	$19.59	$18.61	$17.63	$16.85	82
			RG55, RG142, RG223, RG400	PE4593	$23.79	$22.60	$21.41	$20.46	83
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4523	$25.39	$24.12	$22.85	$21.84	84
		Solder/Solder	RG405, PE-SR405FL, PE-SR405FLJ	PE45119	$11.99	$11.39	$10.79	$10.31	85
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4366	$32.99	$31.34	$29.69	$28.37	86
	Plug, Bulkhead Mount								
Terminal		Solder	Solder Cup with .177 inch D Hole	PE4288	$48.39	$45.97	$43.55	$41.62	87
	Plug Right Angle								
Cable Connectors		Clamp/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE4358	$25.39	$24.12	$22.85	$21.84	88
			RG174, RG316, RG188	PE4260	$44.59	$42.36	$40.13	$38.35	89
			RG178, RG196	PE4261	$50.99	$48.44	$45.89	$43.85	90
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4052	$13.59	$12.91	$12.23	$11.69	91
			RG178, RG196	PE4159	$27.19	$25.83	$24.47	$23.38	92
			RG188-DS, RG316-DS	PE44818	$20.99	$19.94	$18.89	$18.05	93
			RG55, RG142, RG223, RG400	PE4595	$27.99	$26.59	$25.19	$24.07	94
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4522	$30.19	$28.68	$27.17	$25.96	95
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4245	$27.99	$26.59	$25.19	$24.07	96
	Jack								
Cable Connectors		Clamp/Solder	PE-SR405AL, PE-SR405FL, RG405	PE4360	$23.19	$22.03	$20.87	$19.94	97
			RG178, RG196	PE4269	$35.19	$33.43	$31.67	$30.26	98
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4096	$20.19	$19.18	$18.17	$17.36	99
			RG178, RG196	PE4926	$34.79	$33.05	$31.31	$29.92	1
			RG188-DS, RG316-DS	PE45158	$17.39	$16.52	$15.65	$14.96	2
PCB Mount		Solder	.042 inch End Launch	PE44132	$12.99	$12.47	$12.08	$11.82	3
			.042 inch End Launch	PE44137	$27.39	$26.02	$24.65	$23.56	4
			.062 inch End Launch	PE44129	$29.39	$27.92	$26.45	$25.28	5
			.062 inch End Launch	PE44135	$25.79	$24.50	$23.21	$22.18	6
			Surface Mount	PE44119	$13.19	$12.53	$11.87	$11.34	7
			Thru Hole with .200 inch x .067 inch Hole Spacing	PE4174	$10.79	$10.25	$9.71	$9.28	8
	Jack, Bulkhead Mount								
Cable Connectors		Clamp/Solder	PE-SR405AL, PE-SR405FL, RG405	PE4362	$24.19	$22.98	$21.77	$20.80	9
			RG174, RG316, RG188 with .177 inch D Hole	PE4276	$24.59	$23.36	$22.13	$21.15	10
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4097	$23.19	$22.03	$20.87	$19.94	11
			RG178, RG196	PE4364	$23.39	$22.22	$21.05	$20.12	12
			RG188-DS, RG316-DS	PE45159	$18.99	$18.04	$17.09	$16.33	13
			RG55, RG141, RG142, RG223, RG400 with .177 inch D Hole	PE44048	$45.39	$43.12	$40.85	$39.04	14
			RG58	PE44094	$36.59	$34.76	$32.93	$31.47	15

Connectors

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

SMB Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
PCB Mount		Solder	Thru Hole with .177 inch D Hole	PE44123	$27.39	$26.29	$25.47	$24.92	16
Terminal			Solder Cup with .177 inch D Hole	PE4167	$10.99	$10.44	$9.89	$9.45	17
			Solder Cup with .177 inch D Hole	PE4170	$19.99	$18.99	$17.99	$17.19	18
	Jack, 2 Hole Flange Mount								
Terminal		Solder	Solder Cup with .328 inch Hole Spacing	PE44139	$40.59	$38.56	$36.53	$34.91	19
	Jack, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .232 inch Hole Spacing	PE44142	$35.19	$33.43	$31.67	$30.26	20
	Jack Right Angle								
PCB Mount		Solder	Surface Mount	PE44121	$30.99	$29.44	$27.89	$26.65	21
			Thru Hole with .200 inch x .067 inch Hole Spacing	PE4177	$15.99	$15.19	$14.39	$13.75	22
	Jack Right Angle, Bulkhead Mount								
PCB Mount		Solder	Thru Hole with .177 inch D Hole	PE44875	$28.79	$27.35	$25.91	$24.76	23
Terminal			Solder Cup with .177 inch D Hole	PE4284	$36.79	$34.95	$33.11	$31.64	24

SMC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4201	$19.59	$18.61	$17.63	$16.85	25
			RG178, RG196	PE4202	$24.59	$23.36	$22.13	$21.15	26
		Crimp/Solder	PE-P195, PE-C195, RG58, RG141, RG303, .195 inch, LMR-195	PE4558	$29.19	$27.73	$26.27	$25.10	27
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4045	$15.39	$14.62	$13.85	$13.24	28
			RG178, RG196	PE4074	$25.19	$23.93	$22.67	$21.66	29
			RG188-DS, RG316-DS	PE45155	$16.99	$16.14	$15.29	$14.61	30
			RG55, RG142, RG223, RG400	PE45396	$29.79	$28.30	$26.81	$25.62	31
		Solder/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44977	$34.79	$33.05	$31.31	$29.92	32
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4367	$20.19	$19.18	$18.17	$17.36	33
	Plug Right Angle								
Cable Connectors		Clamp/Solder	PE-SR405AL, PE-SR405FL, RG405	PE4359	$55.99	$53.19	$50.39	$48.15	34
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4262	$23.19	$22.03	$20.87	$19.94	35
			RG178, RG196	PE4263	$19.99	$18.99	$17.99	$17.19	36
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4051	$22.79	$21.65	$20.51	$19.60	37
			RG178, RG196	PE4160	$23.79	$22.60	$21.41	$20.46	38
			RG316-DS, RG188-DS	PE44876	$21.19	$20.13	$19.07	$18.22	39
			RG55, RG142, RG223, RG400	PE4596	$27.99	$26.59	$25.19	$24.07	40
			RG58, LMR-195	PE45193	$26.39	$25.07	$23.75	$22.70	41

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

SMC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4246	$75.99	$72.95	$70.67	$69.15	42
	Jack								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188	PE4270	$42.99	$40.84	$38.69	$36.97	43
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4094	$24.59	$23.36	$22.13	$21.15	44
			RG188-DS, RG316-DS	PE45156	$21.99	$20.89	$19.79	$18.91	45
PCB Mount		Solder	.042 inch End Launch	PE44138	$21.19	$20.34	$19.71	$19.28	46
			.062 inch End Launch	PE44130	$63.99	$60.79	$57.59	$55.03	47
			.062 inch End Launch	PE44136	$33.59	$31.91	$30.23	$28.89	48
			Surface Mount	PE44120	$23.59	$22.41	$21.23	$20.29	49
			Thru Hole with .200 inch x .067 inch Hole Spacing	PE4175	$12.99	$12.34	$11.69	$11.17	50
	Jack, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188 with .177 inch D Hole	PE4278	$41.19	$39.13	$37.07	$35.42	51
			RG178, RG196 with .177 inch D Hole	PE4279	$41.19	$39.13	$37.07	$35.42	52
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch with .177 inch D Hole	PE4095	$27.39	$26.02	$24.65	$23.56	53
			RG178, RG196	PE4365	$41.39	$39.32	$37.25	$35.60	54
			RG188-DS, RG316-DS with .177 inch D Hole	PE45157	$20.79	$19.75	$18.71	$17.88	55
			RG55, RG141, RG142, RG223, RG400	PE44047	$33.79	$32.10	$30.41	$29.06	56
			RG58	PE44095	$33.19	$31.53	$29.87	$28.54	57
		Solder/Solder	RG405, PE-SR405FL, PE-SR405AL with .177 inch D Hole	PE45210	$50.99	$48.95	$47.42	$46.40	58
PCB Mount		Solder	.062 inch End Launch	PE44848	$38.19	$36.28	$34.37	$32.84	59
			Thru Hole	PE45147	$30.79	$29.25	$27.71	$26.48	60
			Thru Hole with .177 inch D Hole	PE44124	$40.99	$38.94	$36.89	$35.25	61
Terminal			Solder Cup with .177 inch D Hole	PE4107	$18.99	$18.04	$17.09	$16.33	62
			Solder Cup with .177 inch D Hole	PE4171	$19.19	$18.23	$17.27	$16.50	63
	Jack, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .232 inch Hole Spacing	PE44143	$29.59	$28.11	$26.63	$25.45	64
	Jack Right Angle								
PCB Mount		Solder	Surface Mount	PE44122	$10.59	$10.06	$9.53	$9.11	65
			Thru Hole with .200 inch x .067 inch Hole Spacing	PE4178	$20.59	$19.56	$18.53	$17.71	66
	Jack Right Angle, Bulkhead Mount								
Terminal		Solder	Solder Cup with .177 inch D Hole	PE4285	$40.39	$38.37	$36.35	$34.74	67

SMP Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
PCB Mount		Solder	.062 inch End Launch	PE44943	$44.19	$41.98	$39.77	$38.00	68
			.092 inch End Launch	PE44942	$53.99	$51.29	$48.59	$46.43	69
			Edge Launch	PE44955	$40.79	$38.75	$36.71	$35.08	70
			End Launch	PE44482	$34.59	$32.86	$31.13	$29.75	71
			End Launch	PE44777	$17.79	$16.90	$16.01	$15.30	72
			End Launch	PE44879	$17.19	$16.33	$15.47	$14.78	73
			End Launch	PE44880	$17.19	$16.33	$15.47	$14.78	74
			Surface Mount	PE44481	$46.39	$44.07	$41.75	$39.90	75

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

SMP Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	PRICE See Web for Volume Pricing	ROW
	Male						
PCB Mount		Solder	Surface Mount	PE44944	$66.99	See Web for Volume Pricing	76
			Surface Mount	PE44946	$37.39		77
			Surface Mount	PE44947	$103.99		78
			Surface Mount	PE44952	$56.99		79
			Surface Mount	PE45278TR1	$45.59		80
			Surface Mount	PE45278TR1500	$34,550.00		81
			Thru Hole	PE44480	$44.59		82
			Thru Hole	PE44775	$19.99		83
			Thru Hole	PE44776	$13.39		84
			Thru Hole	PE44840	$13.39		85
			Thru Hole	PE44849	$17.79		86
			Thru Hole	PE44910	$42.59		87
			Thru Hole	PE44936	$48.19		88
			Thru Hole	PE44937	$50.99		89
			Thru Hole	PE44940	$83.99		90
			Thru Hole	PE44957	$54.99		91
			Thru Hole	PE44958	$61.99		92
			Thru Hole	PE44959	$64.99		93
			Thru Hole	PE44960	$37.59		94
			Thru Hole	PE44965	$38.99		95
			Thru Hole	PE44966	$50.99		96
			Thru Hole	PE44967	$39.79		97
			Thru Hole with .100 inch x .031 inch Hole Spacing	PE44348	$42.39		98
Shroud		None	None	PE44932	$24.59		99
Terminal		Solder	Pin	PE44779	$27.19		1
			Pin	PE44780	$27.59		2
			Pin	PE44918	$43.59		3
			Pin	PE44919	$44.79		4
			Pin	PE44920	$33.79		5
			Pin	PE44921	$38.59		6
			Pin	PE44922	$44.79		7
			Pin	PE44923	$40.39		8
			Pin	PE44924	$42.59		9
			Pin	PE44925	$37.19		10
			Pin	PE44926	$41.39		11
			Pin	PE44927	$35.79		12
			Pin	PE44928	$44.39		13
			Pin	PE44930	$35.79		14
			Pin	PE44933	$51.99		15
			Pin	PE44945	$62.99		16
	Male, Bulkhead Mount						
Cable Connectors		Solder/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44961	$48.19	See Web for Volume Pricing	17
			RG405, PE-SR405FL, PE-SR405FLJ	PE45126	$43.39		18
			RG405, RG405 Tinned, PE-SR405FL, PE-SR405AL, PE-SR405FLJ, PE-SR405TN with 4.83 mm Diameter	PE44483	$61.99		19
	Male, 2 Hole Flange Mount						
Cable Connectors		Solder/Solder	RG405, PE-SR405FL, PE-SR405FLJ	PE45127	$45.99		20
Shroud		None	None	PE44935	$22.79		21
			None	PE44907	$22.39		22
			None	PE44916	$23.59		23
			None	PE44948	$24.19		24
			None	PE44949	$23.99		25
			None	PE44950	$24.59		26
			None	PE44951	$30.39		27
Terminal		Solder	Pin	PE44938	$57.99		28

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

SMP Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male, Thread-In								
Shroud		None	None	PE44953	$30.99	$29.44	$27.89	$26.65	29
Terminal		Solder	Pin	PE44909	$53.99	$51.29	$48.59	$46.43	30
			Pin	PE44912	$40.79	$38.75	$36.71	$35.08	31
			Pin	PE44931	$64.99	$61.74	$58.49	$55.89	32
			Pin	PE44956	$91.99	$87.39	$82.79	$79.11	33
			Pin	PE44963	$50.99	$48.44	$45.89	$43.85	34
			Pin	PE44964	$81.99	$77.89	$73.79	$70.51	35
	Male Right Angle								
PCB Mount		Solder	Thru Hole	PE44934	$73.99	$70.29	$66.59	$63.63	36
	Female								
Cable Connectors		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE45277	$6.19	$5.94	$5.76	$5.63	37
		Solder/Solder	.086 Microporous	PE44917	$37.59	$35.71	$33.83	$32.33	38
			PE-047SR, PE-SR047AL, PE-SR047FL	PE44785	$32.19	$30.58	$28.97	$27.68	39
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44786	$29.39	$27.92	$26.45	$25.28	40
			RG178, RG196	PE44655	$66.99	$63.64	$60.29	$57.61	41
			RG178, RG196	PE45287	$13.59	$12.91	$12.23	$11.69	42
			RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ	PE45285	$13.39	$12.72	$12.05	$11.52	43
PCB Mount		Solder	Thru Hole	PE44939	$86.99	$82.64	$78.29	$74.81	44
	Female Right Angle								
Cable Connectors		Crimp/Solder	RG178, RG196	PE45290	$13.39	$12.72	$12.05	$11.52	45
			RG316, RG174, LMR-100	PE45128	$17.79	$16.90	$16.01	$15.30	46
		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE45249	$17.19	$16.33	$15.47	$14.78	47
			RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ	PE45248	$14.19	$13.48	$12.77	$12.20	48
			RG405, PE-SR405FL, PE-SR405FLJ	PE44915	$36.99	$35.14	$33.29	$31.81	49
		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44274	$68.99	$65.54	$62.09	$59.33	50
			PE-047SR, PE-SR047FL, PE-SR047AL	PE44911	$42.79	$40.65	$38.51	$36.80	51
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44275	$44.19	$41.98	$39.77	$38.00	52
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44908	$47.19	$44.83	$42.47	$40.58	53
			RG178, RG196	PE44914	$50.99	$48.44	$45.89	$43.85	54
			RG405, PE-SR405FL, PE-SR405FLJ	PE44913	$74.99	$71.24	$67.49	$64.49	55

SSMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE44379	$32.99	$31.34	$29.69	$28.37	56
			RG178, RG196	PE44381	$37.39	$35.52	$33.65	$32.16	57
			RG188-DS, RG316-DS	PE44416	$31.79	$30.20	$28.61	$27.34	58
		Solder (Without Contact)	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405	PE44382	$33.79	$32.10	$30.41	$29.06	59
		Solder/Solder	PE-034SR	PE44440	$38.39	$36.47	$34.55	$33.02	60
			PE-047SR, PE-SR047AL, PE-SR047FL	PE44441	$45.59	$43.31	$41.03	$39.21	61
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405	PE44383	$46.19	$43.88	$41.57	$39.72	62
			RG174, RG316, RG188	PE4184	$32.59	$30.96	$29.33	$28.03	63
			RG178, RG196	PE4199	$35.39	$33.62	$31.85	$30.44	64

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

SSMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE44430	$33.39	$31.72	$30.05	$28.72	65
	Male, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .232 inch Hole Spacing	PE44432	$34.59	$32.86	$31.13	$29.75	66
	Male Right Angle								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE44378	$39.19	$37.23	$35.27	$33.70	67
			RG178, RG196	PE44380	$73.99	$70.29	$66.59	$63.63	68
			RG188-DS, RG316-DS	PE44418	$45.19	$42.93	$40.67	$38.86	69
		Solder/Solder	PE-034SR	PE44420	$73.99	$70.29	$66.59	$63.63	70
			PE-047SR, PE-SR047AL, PE-SR047FL	PE44421	$77.99	$74.09	$70.19	$67.07	71
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405	PE44384	$53.99	$51.29	$48.59	$46.43	72
			RG174, RG316, RG188	PE44401	$45.99	$43.69	$41.39	$39.55	73
			RG178, RG196	PE44402	$44.19	$42.42	$41.10	$40.21	74
			RG188-DS, RG316-DS	PE44419	$39.19	$37.23	$35.27	$33.70	75
	Female								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE44385	$34.79	$33.05	$31.31	$29.92	76
			RG178, RG196	PE44386	$61.99	$58.89	$55.79	$53.31	77
			RG188-DS, RG316-DS	PE44422	$36.39	$34.57	$32.75	$31.30	78
		Solder/Solder	PE-034SR	PE44424	$44.99	$42.74	$40.49	$38.69	79
			PE-047SR, PE-SR047AL, PE-SR047FL	PE44425	$42.99	$40.84	$38.69	$36.97	80
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405	PE44387	$38.59	$36.66	$34.73	$33.19	81
			RG174, RG316, RG188	PE44403	$34.39	$32.67	$30.95	$29.58	82
			RG178, RG196	PE44404	$38.19	$36.28	$34.37	$32.84	83
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE44391	$42.99	$40.84	$38.69	$36.97	84
	Female, Bulkhead Mount								
Cable Connectors		Crimp/Solder	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100A-FR, PE-C100, PE-B100 with .177 inch D Hole	PE44388	$57.99	$55.09	$52.19	$49.87	85
			RG178, RG196 with .177 inch D Hole	PE44389	$51.99	$49.39	$46.79	$44.71	86
			RG188-DS, RG316-DS with .177 inch D Hole	PE44426	$38.99	$37.04	$35.09	$33.53	87
		Solder/Solder	PE-034SR with .177 inch D Hole	PE44428	$59.99	$56.99	$53.99	$51.59	88
			PE-047SR, PE-SR047AL, PE-SR047FL with .177 inch D Hole	PE44429	$64.99	$61.74	$58.49	$55.89	89
			PE-SR405AL, PE-SR405FL, RG405 with .177 inch D Hole	PE44390	$45.59	$43.31	$41.03	$39.21	90
			RG174, RG316, RG188 with .177 inch D Hole	PE44405	$32.99	$31.34	$29.69	$28.37	91
			RG178, RG196 with .177 inch D Hole	PE44406	$36.39	$34.57	$32.75	$31.30	92
			RG188-DS, RG316-DS with .177 inch D Hole	PE44427	$32.39	$30.77	$29.15	$27.86	93
PCB Mount		Solder	.042 inch End Launch	PE45405	$34.39	$32.67	$30.95	$29.58	94
			.062 inch End Launch	PE45406	$34.39	$32.67	$30.95	$29.58	95
Terminal			Solder Cup with .177 inch D Hole	PE44393	$40.39	$38.37	$36.35	$34.74	96
			Turret with .177 inch D Hole	PE44392	$48.19	$45.78	$43.37	$41.44	97
	Female, 2 Hole Flange Mount								
Cable Connectors		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL with .328 inch Hole Spacing	PE44436	$57.99	$55.09	$52.19	$49.87	98
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405 with .328 inch Hole Spacing	PE44437	$34.59	$32.86	$31.13	$29.75	99
Terminal		Solder	Pin with .328 inch Hole Spacing	PE44433	$61.99	$58.89	$55.79	$53.31	1
			Solder Cup with .328 inch Hole Spacing	PE44395	$61.99	$58.89	$55.79	$53.31	2
	Female, 4 Hole Flange Mount								
Cable Connectors		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL with .232 inch Hole Spacing	PE44438	$58.99	$56.04	$53.09	$50.73	3
			PE-SR405AL, PE-SR405FL, RG405 with .232 inch Hole Spacing	PE44439	$49.39	$46.92	$44.45	$42.48	4

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

SSMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
Terminal		Solder	Pin with .232 inch Hole Spacing	PE44434	$56.99	$54.14	$51.29	$49.01	5
			Solder Cup with .232 inch Hole Spacing	PE44394	$47.79	$45.40	$43.01	$41.10	6
	Female Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE44435	$81.99	$77.89	$73.79	$70.51	7

SSMB Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Jack								
Cable Connectors		Crimp/Solder	RG178, RG196	PE4019	$37.59	$35.71	$33.83	$32.33	8
PCB Mount		Solder	Thru Hole with .100 inch x .031 inch Hole Spacing	PE4340	$20.39	$19.37	$18.35	$17.54	9
	Jack Right Angle								
PCB Mount		Solder	Thru Hole with .100 inch x .031 inch Hole Spacing	PE4341	$37.19	$35.33	$33.47	$31.98	10
	Jack, 4 Hole Flange Mount								
Terminal		Solder	Tab with .164 inch x .067 inch Hole Spacing	PE44455	$32.79	$31.15	$29.51	$28.20	11
	Jack, Bulkhead Mount								
Cable Connectors		Crimp/Solder	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100A-FR, PE-C100, PE-B100 with .126 inch D Hole	PE4336	$50.99	$48.44	$45.89	$43.85	12
			RG178, RG196 with .126 inch D Hole	PE4337	$44.39	$42.17	$39.95	$38.18	13
			RG316-DS, RG188-DS with .126 inch D Hole	PE44842	$39.19	$37.23	$35.27	$33.70	14
Terminal		Solder	Turret with .126 inch D Hole	PE4338	$32.59	$30.96	$29.33	$28.03	15
			Turret with .126 inch D Hole	PE4339	$33.79	$32.10	$30.41	$29.06	16
	Plug								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4017	$45.59	$43.31	$41.03	$39.21	17
			RG188-DS, RG316-DS	PE45153	$36.99	$35.14	$33.29	$31.81	18
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG174, RG179, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE4334	$69.99	$66.49	$62.99	$60.19	19
			RG178, RG196	PE45195	$27.19	$25.83	$24.47	$23.38	20
			RG188-DS, RG316-DS	PE45162	$36.39	$34.93	$33.84	$33.11	21

SSMC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Clamp/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE45366	$33.19	$31.53	$29.87	$28.54	22
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE45365	$28.59	$27.16	$25.73	$24.59	23
		Crimp/Solder	LMR-100A, RG188, RG174, PE-C100-LSZH, PE-B100, LMR-100A-FR, RG316	PE45491	$32.59	$30.96	$29.33	$28.03	24
			RG178, RG196	PE45490	$34.59	$32.86	$31.13	$29.75	25
			RG316, RG174, RG188	PE45209	$19.99	$18.99	$17.99	$17.19	26

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

SSMC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	PRICE See Web for Volume Pricing	ROW
	Plug Right Angle						
Cable Connectors		Crimp/Solder	RG178, RG196	PE45496	$24.59		27
			RG316, RG188, RG174, PE-C100-LSZH, PE-B100, LMR-100A-FR, LMR-100A	PE45497	$28.19		28
			RG316-DS, RG188-DS	PE45498	$27.19		29
		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE45385	$31.79		30
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE45384	$30.39		31
PCB Mount		Solder	Thru Hole	PE45379	$36.99		32
	Jack						
PCB Mount		Solder	Thru Hole	PE45376	$25.19	See Web for Volume Pricing	33
	Jack, Bulkhead Mount						
Cable Connectors		Clamp/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE45371	$31.59		34
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE45370	$22.79		35
		Crimp/Solder	RG-178, RG-196	PE45493	$30.39		36
			RG316, RG188	PE45494	$29.99		37
Terminal		Solder	Turret	PE45375	$24.39		38
			Turret	PE45390	$22.59		39
	Jack, 2 Hole Flange Mount						
Terminal		Solder	Solder Cup	PE45380	$135.99		40
	Jack, 4 Hole Flange Mount						
Terminal		Solder	Solder Cup	PE45391	$79.99		41
	Jack Right Angle						
PCB Mount		Solder	Surface Mount	PE45377	$34.99	See Web for Volume Pricing	42
	Jack Right Angle, Bulkhead Mount						
Cable Connectors		Crimp/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE45387	$42.19		43
			RG178, RG196	PE45499	$27.19		44
		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE45388	$46.99		45
PCB Mount		Solder	Turret	PE45389	$53.99		46
Terminal			Turret	PE45378	$48.99		47

Connectors

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

TNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	PRICE See Web for Volume Pricing	ROW
	Male						
Cable Connectors		Clamp/Solder	PE-C200	PE44061	$21.59	See Web for Volume Pricing	48
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE4449	$27.19		49
			PE-P142LL	PE44815	$84.99		50
			PE-P160LL	PE45443	$94.99		51
			PE-P300LL	PE44810	$129.99		52
			PE-SR402AL, PE-SR402FL, RG402	PE4143	$29.59		53
			PE-SR405AL, PE-SR405FL, RG405	PE4142	$26.99		54
			RG174, RG316, RG188	PE4303	$20.59		55
			RG178, RG196	PE4448	$25.79		56
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG215, RG216*	PE4088	$26.19		57
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4067	$33.99		58
			RG59*, RG62*, RG71	PE4154	$21.59		59
			RG8X, PE-C240, .240 inch, B7808A, LMR-240	PE45437	$27.99		60
		Crimp/Crimp	PE-C200, LMR-200	PE44804	$13.39		61
			RG188-DS, RG316-DS	PE45161	$26.99		62
			RG55, RG142, RG223, RG400	PE4047	$17.39		63
		Crimp/ Non-Solder Contact	LMR-200, PE-C200	EZ-200-TM-X	$21.79		64
			LMR-240, PE-C240	EZ-240-TM-X	$15.19		65
			LMR-400, PE-C400, PE-B400, PE-B405	EZ-400-TM-X	$13.99		66
			LMR-600, PE-C600	EZ-600-TM-X	$21.19		67
		Crimp/Solder	LMR-100A-PVC, PE-C100, RG174, RG188, RG316	SC-100-TM-D	$20.19		68
			LMR-195, PE-C195	TC-195-TM-X	$16.19		69
			LMR-240, PE-C240	TC-240-TM-X	$12.59		70
			LMR-400, PE-C400	TC-400-TM-X	$12.39		71
			PE-C200	PE44062	$23.79		72
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44634	$16.99		73
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44293	$46.99		74
			RG122, RG58 Plenum, RG58-P	PE45065	$8.69		75
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE45527	$18.59		76
			RG213, RG8	PE4446	$25.39		77
			RG214, RG9, RG225, RG393	PE4447	$38.99		78
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4156	$11.19		79
			RG59*, RG62*, RG71	PE4071	$17.19		80
		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE4975	$36.99		81
			PE-SR401AL, PE-SR401FL, RG401	PE4909	$92.99		82
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44709	$19.99		83
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402 with .480 inch D Hole	PE4648	$40.39		84
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44708	$19.99		85
			PE-SR405AL, PE-SR405FL, RG405	PE4649	$37.39		86
	Male, 4 Hole Flange Mount						
Terminal		Solder	Pin with .531 inch Hole Spacing	PE44654	$94.99		87
			Solder Cup with .531 inch Hole Spacing	PE4470	$28.42		88
	Male Right Angle						
Cable Connectors		Clamp/Solder	PE-P142LL	PE44812	$185.99		89
			PE-P160LL	PE45445	$167.99		90
			RG174, RG316, RG188	PE4454	$27.39		91
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4146	$49.39		92
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4054	$35.19		93
			RG59*, RG62*	PE4452	$60.99		94
		Crimp/Crimp	RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4451	$37.19		95

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

TNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc. Price	PRICE See Web for Volume Pricing	ROW
	Male Right Angle						
Cable Connectors		Crimp/Solder	LMR-400, PE-C400	TC-400-TM-RA-D	$26.39	See Web for Volume Pricing	96
			PE-C200, LMR-200	PE44846	$25.79		97
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44635	$32.19		98
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE4455	$35.19		99
			RG188-DS, RG316-DS	PE45174	$30.59		1
			RG55, RG141, RG142, RG223, RG400	PE4450	$22.99		2
		Solder/Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44711	$22.99		3
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44710	$21.19		4
	Sexless						
Cable Connectors		Accessories	RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4022	$2.83		5
	Female						
Cable Connectors		Clamp/Solder	PE-SR402AL, PE-SR402FL, RG402	PE4145	$29.59	See Web for Volume Pricing	6
			PE-SR405AL, PE-SR405FL, RG405	PE4144	$29.59		7
			RG174, RG316, RG188	PE4461	$21.19		8
			RG178, RG196	PE4463	$23.79		9
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4155	$50.99		10
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4068	$18.79		11
			RG59*, RG62*, RG71	PE4460	$20.99		12
		Crimp/Solder	PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44636	$25.19		13
			RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE4462	$27.39		14
			RG316, RG174, LMR-100	PE45143	$13.59		15
			RG55, RG142, RG223, RG400	PE4457	$20.19		16
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4458	$21.39		17
			RG59*, RG62*, RG71	PE4459	$22.99		18
		Solder	LMR-400, LMR-400-DB, LMR-400-UF, PE-B400, PE-B405, PE-C400	PE45639	$8.09		19
		Solder/Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44713	$19.99		20
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44712	$17.19		21
	Female, Bulkhead Mount						
Cable Connectors		Clamp/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44897	$43.19	See Web for Volume Pricing	22
			PE-P142LL	PE44811	$125.99		23
			PE-P160LL	PE45444	$129.99		24
			PE-SR402AL, PE-SR402FL, RG402 with .480 inch D Hole	PE4150	$34.39		25
			PE-SR405AL, PE-SR405FL, RG405 with .480 inch D Hole	PE4149	$34.39		26
			RG174, RG316, RG188 with .480 inch D Hole	PE4304	$28.99		27
			RG178, RG196 with .480 inch D Hole	PE4467	$27.39		28
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, PE-C195, PE-P195 with .480 inch D Hole	PE4152	$24.59		29
			RG59*, RG62*, RG71 with .480 inch D Hole	PE4464	$41.39		30
		Crimp/Solder	RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE44899	$77.99		31
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE44900	$78.99		32
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch with .480 inch D Hole	PE4466	$33.79		33
			RG188-DS, RG316-DS with .480 inch D Hole	PE45177	$29.99		34
			RG55, RG142, RG223, RG400 with .480 inch D Hole	PE4153	$25.79		35
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch with .480 inch D Hole	PE4151	$28.59		36
			RG59*, RG62* with .480 inch D Hole	PE4465	$32.19		37

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

TNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, Bulkhead Mount								
Cable Connectors		Solder	RG178, RG196	PE45132	$29.99	$28.49	$26.99	$25.79	38
		Solder/Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44715	$24.19	$22.98	$21.77	$20.80	39
			PE-SR402AL, PE-SR402FL, RG402 with .480 inch D Hole	PE4148	$91.99	$87.39	$82.79	$79.11	40
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44714	$24.39	$23.17	$21.95	$20.98	41
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44898	$64.99	$61.74	$58.49	$55.89	42
PCB Mount		Solder	Edge Mount	PE44894	$84.99	$80.74	$76.49	$73.09	43
Terminal			Eyelet with .350 inch D Hole	PE4305	$43.39	$41.22	$39.05	$37.32	44
			Eyelet with .480 inch D Hole	PE4469	$56.99	$54.14	$51.29	$49.01	45
			None	PE45130	$16.99	$16.14	$15.29	$14.61	46
			Solder Cup with .350 inch D Hole	PE4065	$19.99	$18.99	$17.99	$17.19	47
			Solder Cup with .350 inch D Hole	PE4306	$17.39	$16.52	$15.65	$14.96	48
			Solder Cup with .410 inch D Hole	PE4063	$31.59	$30.01	$28.43	$27.17	49
			Solder Cup with .480 inch D Hole	PE4468	$24.79	$23.55	$22.31	$21.32	50
	Female, 4 Hole Flange Mount								
Cable Connectors		Clamp/Solder	RG316-DS, RG188-DS	PE44901	$50.99	$48.44	$45.89	$43.85	51
Terminal		Solder	Solder Cup with .500 inch Hole Spacing	PE4064SP	$28.79	$27.35	$25.91	$24.76	52
			Solder Cup with .500 inch Threaded Hole Spacing	PE4064	$19.59	$18.61	$17.63	$16.85	53
	Female Right Angle								
PCB Mount		Solder/Solder	Thru Hole with .380 inch x .083 inch Hole Spacing	PE44659	$22.19	$21.08	$19.97	$19.08	54
	Female Right Angle, Bulkhead Mount								
Cable Connectors		Crimp/Solder	PE-C200, LMR-200 with .480 inch D Hole	PE44847	$29.39	$27.92	$26.45	$25.28	55
PCB Mount		Solder	Surface Mount	PE44892	$86.99	$82.64	$78.29	$74.81	56
Terminal			Solder Cup with .361 inch D Hole	PE4471	$41.39	$39.32	$37.25	$35.60	57

Reverse Polarity TNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	PE-B400, PE-B405	PE4674	$29.59	$28.11	$26.63	$25.45	58
			PE-SR402AL, PE-SR402FL, RG402	PE4670	$30.79	$29.25	$27.71	$26.48	59
			PE-SR405AL, PE-SR405FL, RG405	PE4672	$31.59	$30.01	$28.43	$27.17	60
			RG174, RG316, RG188	PE4667	$29.19	$27.73	$26.27	$25.10	61
			RG178, RG196	PE4669	$26.19	$24.88	$23.57	$22.52	62
			RG213, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4659	$32.19	$30.58	$28.97	$27.68	63
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4662	$19.99	$18.99	$17.99	$17.19	64
			RG59*, RG62*, RG71	PE4665	$19.99	$18.99	$17.99	$17.19	65
		Crimp/Crimp	LMR-200, PE-C200	PE45283	$22.79	$21.65	$20.51	$19.60	66

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

Reverse Polarity TNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Crimp/Solder	PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44670	$16.99	$16.14	$15.29	$14.61	67
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44672	$32.79	$31.15	$29.51	$28.20	68
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4668	$35.39	$33.97	$32.91	$32.20	69
			RG188-DS, RG316-DS	PE45180	$29.99	$28.79	$27.89	$27.29	70
			RG213, RG8	PE4660	$29.39	$27.92	$26.45	$25.28	71
			RG214, RG9, RG225, RG393	PE4661	$33.39	$31.72	$30.05	$28.72	72
			RG55, RG141, RG142, RG223, RG400	PE4663	$20.39	$19.37	$18.35	$17.54	73
			RG58	PE4664	$17.59	$16.71	$15.83	$15.13	74
			RG59*, RG62*, RG71	PE4666	$20.59	$19.56	$18.53	$17.71	75
		Solder/Solder	PE-SR402AL, PE-SR402FL, RG402	PE4671	$42.39	$40.27	$38.15	$36.46	76
			PE-SR405AL, PE-SR405FL, RG405	PE4673	$62.99	$59.84	$56.69	$54.17	77
	Male, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .531 inch Hole Spacing	PE4708	$32.59	$30.96	$29.33	$28.03	78
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG178, RG196	PE4682	$34.79	$33.05	$31.31	$29.92	79
			RG316, RG174, RG188	PE4680	$32.39	$30.77	$29.15	$27.86	80
			RG58, RG55, RG141, RG142, RG223, RG400	PE4676	$44.99	$42.74	$40.49	$38.69	81
			RG59*, RG62*	PE4679	$38.99	$37.04	$35.09	$33.53	82
		Crimp/Solder	RG316, RG174, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4681	$37.99	$36.09	$34.19	$32.67	83
			RG55, RG141, RG142, RG223, RG400	PE4677	$32.19	$30.58	$28.97	$27.68	84
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4678	$35.79	$34.00	$32.21	$30.78	85
	Female								
Cable Connectors		Clamp/Solder	PE-SR402AL, PE-SR402FL, RG402	PE4692	$29.19	$27.73	$26.27	$25.10	86
			PE-SR405AL, PE-SR405FL, RG405	PE4693	$30.19	$28.68	$27.17	$25.96	87
			RG178, RG196	PE4691	$23.59	$22.41	$21.23	$20.29	88
			RG213, RG8, RG215, RG225, RG214, RG393	PE4683	$57.99	$55.09	$52.19	$49.87	89
			RG316, RG174, RG188	PE4689	$22.59	$21.46	$20.33	$19.43	90
			RG58, RG55, RG141, RG142, RG223, RG400	PE4684	$25.79	$24.50	$23.21	$22.18	91
			RG59*, RG62*	PE4688	$30.59	$29.06	$27.53	$26.31	92
		Crimp/ Non-Solder Contact	LMR-200, PE-C200	EZ-200-TF-RP	$19.19	$19.19	$19.19	$19.19	93
		Crimp/Solder	PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44671	$25.59	$24.31	$23.03	$22.01	94
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44673	$22.79	$21.65	$20.51	$19.60	95
			RG316, RG174, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4690	$30.39	$28.87	$27.35	$26.14	96
			RG55, RG142, RG223, RG400	PE4685	$20.99	$19.94	$18.89	$18.05	97
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4686	$23.79	$22.60	$21.41	$20.46	98
			RG59*, RG62*	PE4687	$25.59	$24.31	$23.03	$22.01	99
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	PE-SR402AL, PE-SR402FL, RG402 with .480 inch D Hole	PE4702	$35.19	$33.43	$31.67	$30.26	1
			PE-SR405AL, PE-SR405FL, RG405 with .480 inch D Hole	PE4703	$34.79	$33.05	$31.31	$29.92	2
			RG178, RG196 with .480 inch D Hole	PE4701	$31.19	$29.63	$28.07	$26.82	3
			RG316, RG174, RG188 with .480 inch D Hole	PE4699	$32.39	$30.77	$29.15	$27.86	4
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, PE-C195, PE-P195 with .480 inch D Hole	PE4694	$30.19	$28.68	$27.17	$25.96	5
		Crimp/Solder	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100A-FR, PE-C100, PE-B100 with .480 inch D Hole	PE4700	$36.19	$34.38	$32.57	$31.12	6
			.195 inch, RG58, RG141, RG303, LMR-195, LMR-195-FR, PE-C195, PE-P195 with .480 inch D Hole	PE4696	$35.99	$34.19	$32.39	$30.95	7
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE44902	$65.99	$62.69	$59.39	$56.75	8
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE44903	$74.99	$71.24	$67.49	$64.49	9

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

Reverse Polarity TNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, Bulkhead Mount								
Cable Connectors		Crimp/Solder	RG188-DS, RG316-DS with .480 inch D Hole	PE45181	$31.59	$30.01	$28.43	$27.17	10
			RG55, RG141, RG142, RG223, RG400 with .480 inch D Hole	PE4695	$27.59	$26.21	$24.83	$23.73	11
Terminal		Solder	Solder Cup with .350 inch D Hole	PE4706	$26.19	$24.88	$23.57	$22.52	12
			Solder Cup with .410 inch D Hole	PE4704	$26.19	$24.88	$23.57	$22.52	13
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .500 inch Threaded Hole Spacing	PE4705	$32.99	$31.34	$29.69	$28.37	14

TNC Torque Wrenches



Type	Bit Hex Size (in.)	Preset Torque (in.-lbs.)	Model No	1-9	10-24	25-49	50+	ROW
TNC	5/8 inch	14 in-lbs	PE5011-4	$409.99	$389.49	$368.99	$352.59	
	9/16 inch	13 in-lbs	PE5011-8	$385.99	$366.69	$347.39	$331.95	
	5/8 inch	12 in-lbs	PE5019-10	$283.99	$269.79	$255.59	$244.23	

UHF Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG215, RG216*	PE44050	$17.79	$16.90	$16.01	$15.30	15
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE44052	$16.39	$15.57	$14.75	$14.10	16
		Crimp/Solder	PE-B400, PE-B405, PE-C400, LMR-400, .400 inch	PE44054	$18.19	$17.28	$16.37	$15.64	17
			RG213, RG215, RG8	PE4295	$22.19	$21.08	$19.97	$19.08	18
			RG214, RG9, RG225, RG393	PE44051	$19.59	$18.61	$17.63	$16.85	19
			RG55, RG141, RG142, RG223, RG400	PE44053	$13.39	$12.72	$12.05	$11.52	20
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4069	$15.79	$15.00	$14.21	$13.58	21
			RG59*, RG62*, RG71	PE4073	$11.99	$11.39	$10.79	$10.31	22
		Solder	RG213, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4020	$20.99	$19.94	$18.89	$18.05	23
			RG59*, RG62*, RG71	PE44828	$18.99	$18.04	$17.09	$16.33	24
	Sexless								
Cable Connectors		Accessories	RG59*, RG62*, RG71	PE4021	$2.59	$2.46	$2.33	$2.23	25
	Female								
Cable Connectors		Clamp/Solder	RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE44055	$21.79	$20.70	$19.61	$18.74	26
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE44056	$22.99	$21.84	$20.69	$19.77	27
		Crimp/Solder	RG55, RG141, RG142, RG223, RG400	PE44057	$17.99	$17.09	$16.19	$15.47	28
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE44058	$22.99	$21.84	$20.69	$19.77	29
	Female, Bulkhead Mount								
Terminal		Solder	Solder Cup with .575 inch D Hole	PE44059	$16.99	$16.14	$15.29	$14.61	30
			Solder Cup with .575 inch D Hole	PE44060	$14.79	$14.05	$13.31	$12.72	31

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

UHF Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, 4 Hole Flange Mount								
Terminal		Field Replaceable	Slotted Contact	PE44719	$68.99	$65.54	$62.09	$59.33	32
		Solder	Solder Cup with .718 inch Hole Spacing	PE45478	$11.19	$10.41	$9.62	$8.95	33

UMCX Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Jack								
PCB Mount		Solder	Surface Mount	PE44594	$2.37	$2.25	$2.13	$2.04	34

75 Ohm 1.0/2.3 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Crimp	BELDEN 1855A	PE45228	$17.19	$16.33	$15.47	$14.78	35
			BELDEN 735A1	PE45227	$15.19	$14.43	$13.67	$13.06	36
			RG179-DS	PE45233	$15.19	$14.43	$13.67	$13.06	37
			RG59*	PE45234	$15.19	$14.43	$13.67	$13.06	38
			RG6-CATV	PE45235	$22.59	$21.46	$20.33	$19.43	39
	Male								
Cable Connectors		Crimp/Solder	Belden 4694R, Belden 1694A, RG6	PE40003	$18.39	$17.47	$16.55	$15.82	40
			Belden 4855R, Belden 1855A	PE40005	$18.19	$17.28	$16.37	$15.64	41
	Jack Right Angle, Bulkhead Mount								
PCB Mount		Solder	Thru Hole	PE45230	$18.79	$17.85	$16.91	$16.16	42
			Thru Hole	PE45237	$22.19	$21.08	$19.97	$19.08	43
	Jack, Bulkhead Mount								
PCB Mount		Solder	End Launch	PE45232	$24.19	$22.98	$21.77	$20.80	44
			Thru Hole	PE45229	$19.79	$18.80	$17.81	$17.02	45
			Thru Hole	PE45231	$21.79	$20.70	$19.61	$18.74	46
	Female								
PCB Mount		Solder	Thru Hole	PE40017	$7.49	$7.12	$6.74	$6.44	47
	Female Right Angle, Bulkhead Mount								
PCB Mount		Solder	Thru Hole	PE40018	$13.19	$12.53	$11.87	$11.34	48

75 Ohm 1.6/5.6 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG179, RG187	PE44262	$22.99	$21.84	$20.69	$19.77	49
			RG59*, RG62*, RG71	PE44263	$21.79	$20.70	$19.61	$18.74	50

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

75 Ohm 1.6/5.6 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug Right Angle								
Cable Connectors		Clamp/Solder	RG179, RG187	PE44264	$23.39	$22.22	$21.05	$20.12	51
	Jack, Bulkhead Mount								
PCB Mount		Solder	Thru Hole with .362 inch Diameter	PE44270	$19.59	$18.61	$17.63	$16.85	52
	Jack Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .052 inch Hole Spacing	PE44271	$22.39	$21.27	$20.15	$19.26	53
	Jack Right Angle, Bulkhead Mount								
Cable Connectors		Crimp/Solder	RG179, RG187 with .362 inch DD Hole	PE44268	$23.39	$22.22	$21.05	$20.12	54

75 Ohm BNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	RG11*, RG144*, RG216*	PE4599	$45.59	$43.31	$41.03	$39.21	55
			RG179, RG187	PE4603	$20.59	$19.56	$18.53	$17.71	56
			RG59*, RG62*, RG71	PE4601	$22.39	$21.27	$20.15	$19.26	57
		Compression	Mini 59, PE-B159	PE44578	$21.39	$20.32	$19.25	$18.40	58
			PE-B159, 1855A, Mini 59	PE44577	$18.99	$18.04	$17.09	$16.33	59
		Crimp/Crimp	RG59*, RG62*, RG71	PE4602	$13.19	$12.53	$11.87	$11.34	60
		Crimp/Solder	1505A	PE44626	$15.39	$14.62	$13.85	$13.24	61
			1505A	PE44631	$7.89	$7.50	$7.10	$6.79	62
			1694A	PE44627	$7.39	$7.02	$6.65	$6.36	63
			1694A	PE44632	$20.59	$19.56	$18.53	$17.71	64
			735A	PE44686	$35.99	$34.19	$32.39	$30.95	65
			7731A	PE44628	$13.19	$12.53	$11.87	$11.34	66
			Belden 150A	PE45117	$12.39	$11.77	$11.15	$10.66	67
			Belden 1694A	PE45116	$16.19	$15.38	$14.57	$13.92	68
			Belden 4694R, Belden 1694A, RG6	PE40001	$9.99	$9.49	$8.99	$8.59	69
			PE-B150, RG180, RG195	PE4633	$20.19	$19.18	$18.17	$17.36	70
			PE-B159, 1855A, Mini 59	PE44584	$20.79	$19.75	$18.71	$17.88	71
			PE-B159, 1855A, Mini 59	PE44625	$16.39	$15.57	$14.75	$14.10	72
			PE-B305	PE4634	$20.99	$19.94	$18.89	$18.05	73
			RG11*, RG216*, RG144*	PE4600	$28.59	$27.16	$25.73	$24.59	74
			RG179, RG187	PE4604	$17.79	$16.90	$16.01	$15.30	75
			RG6	PE4598	$10.19	$9.68	$9.17	$8.76	76
	Male, Bulkhead Mount								
Terminal		Solder	Solder Cup with .350 inch D Hole	PE4627	$28.59	$27.16	$25.73	$24.59	77
	Male, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .531 inch Hole Spacing	PE4625	$26.59	$25.26	$23.93	$22.87	78

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

75 Ohm BNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG179, RG187	PE4609	$66.99	$63.64	$60.29	$57.61	79
			RG59*, RG62*, RG71	PE4607	$59.99	$56.99	$53.99	$51.59	80
			RG6	PE4605	$47.59	$45.21	$42.83	$40.93	81
		Crimp/Solder	RG179, RG187	PE4610	$29.99	$28.49	$26.99	$25.79	82
			RG59*, RG62*, RG71	PE4608	$44.19	$41.98	$39.77	$38.00	83
	Female								
Cable Connectors		Clamp/Solder	RG179, RG187	PE4615	$36.39	$34.93	$33.84	$33.11	84
			RG59*	PE4613	$27.79	$26.40	$25.01	$23.90	85
			RG6	PE4611	$54.99	$52.24	$49.49	$47.29	86
		Crimp/Solder	735A	PE44688	$34.59	$32.86	$31.13	$29.75	87
			RG179, RG187	PE4616	$25.59	$24.31	$23.03	$22.01	88
PCB Mount		Solder	End Launch	PE44619	$13.59	$12.91	$12.23	$11.69	89
			Thru Hole	PE40006	$5.59	$5.31	$5.03	$4.81	90
			Thru Hole	PE40010	$7.99	$7.59	$7.19	$6.87	91
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG179, RG187 with .480 inch D Hole	PE4639	$44.19	$42.42	$41.10	$40.21	92
			RG59*, RG62*, RG71 with .480 inch D Hole	PE4637	$46.39	$44.07	$41.75	$39.90	93
		Crimp/Solder	735A with .480 inch D Hole	PE44687	$36.99	$35.14	$33.29	$31.81	94
			PE-B150, RG180, RG195 with .480 inch D Hole	PE4641	$35.99	$34.19	$32.39	$30.95	95
			PE-B159, 1855A, Mini 59 with .480 inch D Hole	PE44587	$29.99	$28.49	$26.99	$25.79	96
			PE-B305 with .480 inch D Hole	PE4642	$41.19	$39.13	$37.07	$35.42	97
			RG179, RG187 with .480 inch D Hole	PE4640	$30.39	$28.87	$27.35	$26.14	98
			RG59*, RG62*, RG71 with .480 inch D Hole	PE4638	$38.59	$36.66	$34.73	$33.19	99
PCB Mount		Solder	0.062" Board Thickness	PE40009	$6.39	$6.07	$5.75	$5.50	1
			0.062" Board Thickness	PE40012	$13.59	$12.91	$12.23	$11.69	2
			End Launch with .500 inch Diameter	PE44620	$21.99	$20.89	$19.79	$18.91	3
Terminal			Solder Cup with .350 inch D Hole	PE4620	$19.19	$18.23	$17.27	$16.50	4
			Solder Cup with .350 inch D Hole	PE4626	$17.39	$16.52	$15.65	$14.96	5
			Solder Cup with .410 inch D Hole	PE4619	$14.19	$13.48	$12.77	$12.20	6
			Turret with .350 inch D Hole	PE4624	$46.59	$44.26	$41.93	$40.07	7
			Turret with .480 inch D Hole	PE4621	$57.99	$55.09	$52.19	$49.87	8
	Female, 4 Hole Flange Mount								
Cable Connectors		Clamp/Solder	RG179, RG187 with .500 inch Threaded Hole Spacing	PE44652	$45.39	$43.12	$40.85	$39.04	9
			RG59*, RG62*, RG71 with .500 inch Threaded Hole Spacing	PE4623	$47.39	$45.02	$42.65	$40.76	10
Terminal		Solder	Solder Cup with .500 inch Hole Spacing	PE4630	$26.19	$24.88	$23.57	$22.52	11
			Solder Cup with .500 inch Threaded Hole Spacing	PE4617	$20.99	$19.94	$18.89	$18.05	12
			Solder Cup with .718 inch Hole Spacing	PE4631	$35.19	$33.43	$31.67	$30.26	13
			Turret with .531 inch Hole Spacing	PE4618	$56.99	$54.14	$51.29	$49.01	14
	Female Right Angle, Bulkhead Mount								
PCB Mount		Solder	0.062" Board Thickness	PE40008	$15.19	$14.43	$13.67	$13.06	15
			Thru Hole	PE40007	$9.79	$9.30	$8.81	$8.42	16
			Thru Hole	PE40011	$15.99	$15.19	$14.39	$13.75	17
Terminal			Solder Cup with .361 inch D Hole	PE4622	$69.99	$66.49	$62.99	$60.19	18
	Female Right Angle, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .531 inch Hole Spacing	PE4628	$33.19	$31.53	$29.87	$28.54	19

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

75 Ohm F Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Compression	PE-B159, 1855A, Mini 59	PE44572	$8.69	$8.26	$7.82	$7.47	20
			PE-B159, 1855A, Mini 59	PE44573	$7.59	$7.21	$6.83	$6.53	21
		Crimp/Crimp	RG59*, RG62*, RG71	PE44317	$7.39	$7.02	$6.65	$6.36	22
			RG6	PE44312	$3.13	$2.97	$2.82	$2.69	23
		Crimp/ Non-Solder Contact	LMR-400-75	EZ-400-FM-75	$32.99	$32.99	$32.99	$32.99	24
		Crimp/Solder	PE-B159, 1855A, Mini 59	PE44582	$7.79	$7.40	$7.01	$6.70	25
			RG11*, RG216*, RG144*	PE44315	$9.09	$8.64	$8.18	$7.82	26
			RG179, RG187	PE45520	$5.39	$5.12	$4.85	$4.64	27
			RG59*, RG62*, RG71	PE44316	$1.89	$1.80	$1.70	$1.63	28
			RG6-CATV	PE44313	$7.39	$7.02	$6.65	$6.36	29
			RG6-CATV	PE44452	$4.47	$4.25	$4.02	$3.84	30
		Twist	RG59*, RG62*, RG71	PE44318	$2.19	$2.08	$1.97	$1.88	31
			RG6	PE44314	$3.43	$3.26	$3.09	$2.95	32
	Male Right Angle								
Cable Connectors		Compression	PE-B159, 1855A, Mini 59	PE44579	$17.59	$16.71	$15.83	$15.13	33
		Crimp/Solder	RG59*, RG62*, RG71	PE44322	$10.59	$10.06	$9.53	$9.11	34
			RG6-CATV	PE44320	$12.59	$11.96	$11.33	$10.83	35
		Twist	RG59*, RG62*, RG71	PE44323	$8.09	$7.69	$7.28	$6.96	36
	Female								
PCB Mount		Solder	Thru Hole with .320 inch x .091 inch Hole Spacing	PE44331	$2.89	$2.75	$2.60	$2.49	37
	Female, Bulkhead Mount								
Cable Connectors		Crimp/Solder	PE-B159, 1855A, Mini 59 with .480 inch D Hole	PE44585	$9.69	$9.21	$8.72	$8.33	38
			RG179, RG187 with .380 inch DD Hole	PE45504	$8.99	$8.63	$8.36	$8.18	39
			RG59*, RG62*, RG71	PE45552	$6.98	$6.63	$6.28	$6.00	40
			RG6-CATV	PE44324	$11.79	$11.20	$10.61	$10.14	41
PCB Mount		Solder	Thru Hole with .340 inch x .091 inch Hole Spacing	PE44332	$7.49	$7.12	$6.74	$6.44	42
Terminal			Tab with .380 inch DD Hole	PE44327	$2.25	$2.14	$2.03	$1.94	43
	Female, 4 Hole Flange Mount								
Terminal		Solder	Pin with .500 inch Hole Spacing	PE44329	$12.79	$12.15	$11.51	$11.00	44
	Female, Thread-In								
Terminal		Solder	Pin with .380 inch Diameter	PE44330	$3.53	$3.35	$3.18	$3.04	45
	Female Right Angle								
PCB Mount		Solder	Thru Hole with .320 inch x .091 inch Hole Spacing	PE44333	$8.99	$8.54	$8.09	$7.73	46

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

75 Ohm F Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female Right Angle, Bulkhead Mount								
PCB Mount		Solder	Surface Mount	PE44895	$21.99	$20.89	$19.79	$18.91	47
			Thru Hole with .350 inch D Hole	PE44334	$10.99	$10.44	$9.89	$9.45	48

75 Ohm HD-BNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Crimp/Solder	Belden 4694R, Belden 1694A, RG6	PE40002	$11.99	$11.39	$10.79	$10.31	49
			Belden 4855R, Belden 1855A	PE40004	$11.79	$11.20	$10.61	$10.14	50
	Female								
PCB Mount		Solder	Thru Hole	PE40016	$9.39	$8.92	$8.45	$8.08	51
	Female, Bulkhead Mount								
PCB Mount		Solder	0.062” Board Thickness	PE40015	$8.29	$7.88	$7.46	$7.13	52
			Thru Hole	PE40013	$9.69	$9.21	$8.72	$8.33	53
	Female Right Angle, Bulkhead Mount								
PCB Mount		Solder	Thru Hole	PE40014	$12.59	$11.96	$11.33	$10.83	54

75 Ohm MCX Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG179, RG187	PE44298	$19.19	$18.23	$17.27	$16.50	55
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG179, RG187	PE45086	$23.19	$22.03	$20.87	$19.94	56
	Jack								
Cable Connectors		Crimp/Solder	RG179, RG187	PE44300	$37.39	$35.52	$33.65	$32.16	57
PCB Mount		Solder	.072 inch End Launch	PE45211	$16.79	$15.95	$15.11	$14.44	58
	Jack Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .055 inch Hole Spacing	PE44304	$22.59	$21.46	$20.33	$19.43	59

Connectors

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

75 Ohm Mini SMB Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	PE-B159, 1855A, Mini 59	PE44588	$29.39	$27.92	$26.45	$25.28	60
			RG179, RG187	PE4993	$24.59	$23.36	$22.13	$21.15	61
			RG59*, RG62*, RG71	PE4994	$37.79	$36.28	$35.14	$34.39	62
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG179, RG187	PE4995	$27.59	$26.21	$24.83	$23.73	63
			RG59*, RG62*, RG71	PE4996	$32.99	$31.34	$29.69	$28.37	64
	Jack								
PCB Mount		Solder	.062 inch End Launch	PE44131	$31.59	$30.01	$28.43	$27.17	65
			Thru Hole with .200 inch x .055 inch Hole Spacing	PE4997	$22.19	$21.08	$19.97	$19.08	66
	Jack, 2 Hole Flange Mount								
Terminal		Solder	Solder Cup with .328 inch Hole Spacing	PE44141	$31.39	$29.82	$28.25	$27.00	67
	Jack Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .055 inch Hole Spacing	PE4998	$30.99	$29.44	$27.89	$26.65	68
	Jack Right Angle, Bulkhead Mount								
PCB Mount		Solder	Thru Hole with .177 inch D Hole	PE44128	$31.79	$30.20	$28.61	$27.34	69

75 Ohm N Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	RG11*, RG144*, RG216*	PE4509	$45.99	$44.15	$42.77	$41.85	70
			RG179, RG187	PE4513	$27.59	$26.21	$24.83	$23.73	71
			RG59*, RG62*, RG71	PE4511	$30.99	$29.44	$27.89	$26.65	72
			RG6	PE4507	$30.39	$28.87	$27.35	$26.14	73
		Crimp/ Non-Solder Contact	LMR-400-75	EZ-400-NMH-75-X	$39.99	$39.99	$39.99	$39.99	74
		Crimp/Solder	RG11*, RG144*, RG216*	PE4510	$32.79	$31.15	$29.51	$28.20	75
			RG179, RG187	PE4656	$47.99	$45.59	$43.19	$41.27	76
			RG59*, RG62*, RG71	PE4512	$31.79	$30.20	$28.61	$27.34	77
			RG6	PE4508	$32.19	$30.58	$28.97	$27.68	78
	Male, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .718 inch Hole Spacing	PE4504	$53.99	$51.29	$48.59	$46.43	79
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG11*, RG144*, RG216*	PE4502	$68.99	$66.23	$64.16	$62.78	80
	Female								
Cable Connectors		Clamp/Solder	RG59*, RG62*, RG71	PE4516	$52.99	$50.34	$47.69	$45.57	81
			RG6	PE4514	$63.99	$61.43	$59.51	$58.23	82

Connectors

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

75 Ohm N Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, Bulkhead Mount								
Terminal		Solder	Solder Cup with .380 inch Diameter	PE4506	$23.99	$22.79	$21.59	$20.63	83
			Solder Cup with .640 inch DD Hole	PE4505	$36.19	$34.38	$32.57	$31.12	84
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .718 inch Hole Spacing	PE4503	$22.59	$21.46	$20.33	$19.43	85

75 Ohm RCA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Compression	Mini 59, PE-B159	PE44576	$9.29	$8.83	$8.36	$7.99	86
			PE-B159, 1855A, Mini 59	PE44574	$17.39	$16.52	$15.65	$14.96	87
		Crimp/Solder	1505A	PE44624	$19.59	$18.61	$17.63	$16.85	88
			1694A	PE44623	$15.99	$15.19	$14.39	$13.75	89
			Mini 59, PE-B159	PE44622	$19.59	$18.61	$17.63	$16.85	90
			PE-B159	PE44583	$18.59	$17.66	$16.73	$15.99	91
	Male Right Angle								
Cable Connectors		Compression	Mini 59, PE-B159	PE44580	$23.39	$22.22	$21.05	$20.12	92
	Female, Bulkhead Mount								
Cable Connectors		Crimp/Solder	PE-B159, 1855A, Mini 59 with .480 inch D Hole	PE44586	$23.59	$22.41	$21.23	$20.29	93

75 Ohm SMB Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Clamp/Solder	RG179, RG187	PE4257	$32.79	$31.15	$29.51	$28.20	94
			RG59*, RG62*, RG71	PE4203	$25.59	$24.31	$23.03	$22.01	95
		Crimp/Solder	RG179, RG187	PE4248	$26.59	$25.26	$23.93	$22.87	96
			RG59*, RG62*, RG71	PE4472	$32.79	$31.15	$29.51	$28.20	97
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4368	$24.39	$23.41	$22.68	$22.19	98
	Plug, Bulkhead Mount								
Terminal		Solder	Solder Cup with .295 inch D Hole	PE4290	$79.99	$75.99	$71.99	$68.79	99
	Plug Right Angle								
Cable Connectors		Clamp/Solder	RG59*, RG62*	PE4264	$51.99	$49.39	$46.79	$44.71	1
		Crimp/Solder	RG179, RG187	PE4251	$35.79	$34.00	$32.21	$30.78	2

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

75 Ohm SMB Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Jack								
Cable Connectors		Clamp/Solder	RG179, RG187	PE4928	$57.99	$55.09	$52.19	$49.87	3
			RG59*, RG62*	PE4272	$44.39	$42.17	$39.95	$38.18	4
		Crimp/Solder	PE-B150, RG180, RG195	PE4163	$26.99	$25.64	$24.29	$23.21	5
			RG179, RG187	PE44872	$46.19	$43.88	$41.57	$39.72	6
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4110	$30.19	$28.68	$27.17	$25.96	7
	Jack, Bulkhead Mount								
Cable Connectors		Crimp/Solder	RG179, RG187 with .285 inch D Hole	PE4255	$61.99	$58.89	$55.79	$53.31	8
Terminal		Solder	Solder Cup with .295 inch D Hole	PE4172	$22.79	$21.65	$20.51	$19.60	9
			Solder Cup with .317 inch Diameter	PE4168	$21.59	$20.51	$19.43	$18.57	10
	Jack Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4179	$29.59	$28.11	$26.63	$25.45	11

75 Ohm SMB Positive Snap Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG179, RG187	PE44443	$41.19	$39.13	$37.07	$35.42	12
			RG59*, RG62*	PE44442	$28.99	$27.54	$26.09	$24.93	13
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG179, RG187	PE44445	$45.19	$42.93	$40.67	$38.86	14
			RG180, RG195	PE44446	$60.99	$57.94	$54.89	$52.45	15

75 Ohm SMC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Clamp/Solder	RG179, RG187	PE4259	$57.99	$55.09	$52.19	$49.87	16
			RG59*, RG62*, RG71	PE4258	$61.99	$58.89	$55.79	$53.31	17
		Crimp/Solder	PE-B150, RG180, RG195	PE4158	$34.59	$32.86	$31.13	$29.75	18
			RG179, RG187	PE4249	$28.59	$27.16	$25.73	$24.59	19
			RG59*, RG62*, RG71	PE4658	$35.99	$34.19	$32.39	$30.95	20
	Plug, Bulkhead Mount								
Terminal		Solder	Solder Cup with .295 inch D Hole	PE4291	$58.99	$56.04	$53.09	$50.73	21
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG180, RG195	PE4162	$47.99	$45.59	$43.19	$41.27	22

Connectors

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

75 Ohm SMC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4293	$56.99	$54.14	$51.29	$49.01	23
	Jack								
Cable Connectors		Clamp/Solder	RG180, RG195	PE4275	$42.19	$40.08	$37.97	$36.28	24
			RG59*, RG62*	PE4274	$50.99	$48.44	$45.89	$43.85	25
		Crimp/Solder	RG179, RG187	PE4254	$45.59	$43.77	$42.40	$41.49	26
			RG180, RG195	PE4164	$38.79	$37.24	$36.07	$35.30	27
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4176	$26.39	$25.33	$24.54	$24.01	28
	Jack, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG179, RG187	PE4906	$56.99	$54.14	$51.29	$49.01	29
			RG180, RG195 with .285 inch D Hole	PE4283	$37.59	$35.71	$33.83	$32.33	30
		Crimp/Solder	RG179, RG187 with .285 inch D Hole	PE4256	$44.79	$42.55	$40.31	$38.52	31
			RG180, RG195 with .177 inch D Hole	PE45205	$44.19	$41.10	$38.00	$35.35	32
Terminal		Solder	Solder Cup with .295 inch D Hole	PE4169	$57.99	$55.09	$52.19	$49.87	33
			Solder Cup with .295 inch D Hole	PE4173	$40.39	$38.37	$36.35	$34.74	34
	Jack Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4180	$50.99	$48.44	$45.89	$43.85	35

75 Ohm TNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	RG11*, RG144*, RG216*	PE44163	$75.99	$72.19	$68.39	$65.35	36
			RG179, RG187	PE44167	$24.19	$22.98	$21.77	$20.80	37
			RG6	PE44161	$34.19	$32.82	$31.80	$31.11	38
		Crimp/Solder	RG11*, RG144*	PE44164	$57.99	$55.09	$52.19	$49.87	39
			RG179, RG187, RG316	PE45687	$35.39	$33.62	$31.85	$30.44	40
			RG59*, RG62*	PE44166	$24.19	$22.98	$21.77	$20.80	41
			RG6	PE44162	$27.79	$26.40	$25.01	$23.90	42
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG11*, RG216* with .480 inch D Hole	PE44174	$59.99	$56.99	$53.99	$51.59	43
			RG179, RG187 with .480 inch D Hole	PE44176	$60.99	$57.94	$54.89	$52.45	44
			RG6 with .480 inch D Hole	PE44173	$56.99	$54.14	$51.29	$49.01	45
Terminal		Solder	Solder Cup with .410 inch D Hole	PE44177	$28.19	$26.78	$25.37	$24.24	46
			Solder Cup with .480 inch D Hole	PE44181	$35.19	$33.43	$31.67	$30.26	47
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .500 inch Threaded Hole Spacing	PE44178	$26.19	$24.88	$23.57	$22.52	48
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG179, RG187	PE44172	$84.99	$80.74	$76.49	$73.09	49
			RG59*, RG62*, RG71	PE44171	$74.99	$71.24	$67.49	$64.49	50

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

BNC Twinax Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Clamp/Solder	RG108, 78 Ohm Twinax	PE4236	$36.99	$35.14	$33.29	$31.81	51
		Crimp/Solder	RG108, 78 Ohm Twinax	PE4234	$28.19	$26.78	$25.37	$24.24	52
	Jack								
Cable Connectors		Clamp/Solder	RG108, 78 Ohm Twinax	PE4237	$46.19	$43.88	$41.57	$39.72	53
		Crimp/Solder	RG108, 78 Ohm Twinax	PE4235	$53.99	$51.29	$48.59	$46.43	54
PCB Mount		Solder	Thru Hole with .687 inch x .500 inch Hole Spacing	PE44115	$40.19	$38.58	$37.38	$36.57	55
	Jack, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG108, 78 Ohm Twinax with .480 inch D Hole	PE44114	$64.99	$61.74	$58.49	$55.89	56
Terminal		Solder	Solder Cup with .350 inch D Hole	PE4238	$29.39	$27.92	$26.45	$25.28	57
	Jack, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .500 inch Threaded Hole Spacing	PE4324	$56.99	$54.14	$51.29	$49.01	58
	Jack Right Angle								
PCB Mount		Solder	Thru Hole with .687 inch x .500 inch Hole Spacing	PE44116	$61.99	$58.89	$55.79	$53.31	59

3/4”-20 Twinax Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	PE-S330	PE4104	$35.59	$33.81	$32.03	$30.61	60
	Female								
Cable Connectors		Clamp/Solder	PE-S330	PE4346	$33.79	$32.10	$30.41	$29.06	61
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .718 inch Hole Spacing	PE4347	$40.99	$38.94	$36.89	$35.25	62
	Female, Bulkhead Mount								
Terminal		Solder	Solder Cup with .720 inch D Hole	PE4105	$34.59	$32.86	$31.13	$29.75	63

Connectors

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

Banana Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG188-DS, RG316-DS	PE45164	$19.99	$18.99	$17.99	$17.19	64
			RG55, RG142, RG223, RG400	PE4089	$13.59	$12.91	$12.23	$11.69	65

Double Banana Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE4301	$14.19	$13.48	$12.77	$12.20	66
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE44145	$18.59	$17.66	$16.73	$15.99	67

LAUNCH PINS






Model No	Description	1-24	25-49	50-99	100+	ROW
PE1015-1	Hermetic seal for 0.23mm (.009inch) field replaceable connector	$20.59	$19.56	$18.53	$17.71	68
PE1015-4	Hermetic seal for 0.3mm (.012inch) field replaceable connector	$10.59	$10.06	$9.53	$9.11	69
PE1015-5	Hermetic seal for 0.3mm (.012inch) field replaceable connector	$8.29	$7.88	$7.46	$7.13	70
PE1015-6	Hermetic seal for 0.38mm (.015inch) field replaceable connector	$8.29	$7.88	$7.46	$7.13	71
PE1015-2	Hermetic Seal Solder Contact with 0.012" Diameter Full Radius Pin, 0.098" Body Diameter and 0.179" Pin Length (HERMETICITY 1E(-8) STD CC/SEC @1ATM)	$8.49	$8.07	$7.64	$7.30	72
PE1015-3	Hermetic Seal Solder Contact with 0.015" Diameter Full Radius Pin, 0.098" Body Diameter and 0.18" Pin Length (HERMETICITY 1E(-8) STD CC/SEC @1ATM)	$8.49	$8.07	$7.64	$7.30	73
PE1017-7	Hermetic Seal Solder Contact with 0.018" Diameter Full Radius Pin, 0.109" Body Diameter and 0.18" Pin Length (HERMETICITY 1E(-8) STD CC/SEC @1ATM)	$10.59	$10.06	$9.53	$9.11	74
PE1015-7	Hermetic Seal Solder Contact with 0.02" Diameter Full Radius Pin, 0.157" Body Diameter and 0.204" Pin Length (HERMETICITY 1E(-8) STD CC/SEC @1ATM)	$9.99	$9.49	$8.99	$8.59	75
PE1017-2	Launch pin & dielectric for 0.23mm (.009inch) field replaceable connector	$11.39	$10.82	$10.25	$9.80	76
PE1017-1	Launch pin & dielectric for 0.23mm (.009inch) field replaceable connector	$10.39	$9.87	$9.35	$8.94	77
PE1017-6	Launch pin & dielectric for 0.38mm (.015inch) field replaceable connector	$6.98	$6.63	$6.28	$6.00	78
PE1017-5	Launch pin & dielectric for 0.38mm (.015inch) field replaceable connector	$6.98	$6.63	$6.28	$6.00	79
PE1017-8	Launch pin & dielectric for 0.51mm (.020inch) field replaceable connector	$7.29	$6.93	$6.56	$6.27	80
PE1017-9	Launch pin & dielectric for 0.51mm (.020inch) field replaceable connector	$5.69	$5.41	$5.12	$4.89	81
PE1017-10	Launch pin & dielectric for 0.91mm (.036inch) field replaceable connector	$5.69	$5.41	$5.12	$4.89	82
PE1017-11	Launch pin & dielectric for 0.91mm (.036inch) field replaceable connector	$5.69	$5.41	$5.12	$4.89	83
PE1017-4	Launch Pin to Pin Contact with 0.012" Diameter Full Radius Pin with 0.159" Pin Length and Dielectric	$7.49	$7.12	$6.74	$6.44	84
PE1017-3	Launch Pin to Pin Contact with 0.012" Diameter Full Radius Pin with 0.255" Pin Length and Dielectric	$7.99	$7.59	$7.19	$6.87	85
PE1016-9	Launch Pin to Tab Contact with 0.015" Diameter Full Radius Pin with 0.16" Pin Length and Dielectric	$12.79	$12.15	$11.51	$11.00	86
PE1016-8	Launch Pin to Tab Contact with 0.015" Diameter Full Radius Pin with 0.225" Pin Length and Dielectric	$9.59	$9.11	$8.63	$8.25	87

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

LAUNCH PINS






Model No	Description	1-24	25-49	50-99	100+	ROW
PE1016-2	Tab pin & dielectric for 0.23mm (.009inch) field replaceable connector	$20.79	$19.75	$18.71	$17.88	88
PE1016-3	Tab pin & dielectric for 0.23mm (.009inch) field replaceable connector	$18.39	$17.47	$16.55	$15.82	89
PE1016-5	Tab pin & dielectric for 0.3mm (.012inch) field replaceable connector	$10.99	$10.44	$9.89	$9.45	90
PE1016-6	Tab pin & dielectric for 0.3mm (.012inch) field replaceable connector	$11.79	$11.20	$10.61	$10.14	91
PE1016-11	Tab pin & dielectric for 0.51mm (.020inch) field replaceable connector	$6.98	$6.63	$6.28	$6.00	92
PE1016-12	Tab pin & dielectric for 0.51mm (.020inch) field replaceable connector	$9.59	$9.11	$8.63	$8.25	93
PE1016-15	Tab pin & dielectric for 0.91mm (.036inch) field replaceable connector	$7.69	$7.31	$6.92	$6.61	94
PE1016-14	Tab pin & dielectric for 0.91mm (.036inch) field replaceable connector	$7.09	$6.74	$6.38	$6.10	95
PE1016-1	Tab pin for 0.23mm (.009inch) field replaceable connector	$14.79	$14.05	$13.31	$12.72	96
PE1016-7	Tab pin for 0.38mm (.015inch) field replaceable connector	$8.48	$8.06	$7.63	$7.29	97
PE1016-4	Tab pin for 0.3mm (.012inch) field replaceable connector	$9.79	$9.30	$8.81	$8.42	98
PE1016-10	Tab pin for 0.51mm (.020inch) field replaceable connector	$5.19	$4.93	$4.67	$4.46	99
PE1016-13	Tab pin for 0.91mm (.036inch) field replaceable connector	$6.69	$6.36	$6.02	$5.75	1

CONNECTOR DUST CAPS

Non-Shorting Caps






Connector	Gender	Compatible With	Chain	Model No	1-24	25-49	50-99	100+	ROW
7/16 DIN	Male	50 Ohm	Yes	PE6057	$54.99	$52.24	$49.49	$47.29	2
	Female		Yes	PE6058	$65.99	$62.69	$59.39	$56.75	3
BNC	Male		Yes	PE6013	$10.99	$10.44	$9.89	$9.45	4
			No	PE6014	$6.59	$6.26	$5.93	$5.67	5
	Female		Yes	PE6015	$9.59	$9.11	$8.63	$8.25	6
			No	PE6108	$17.39	$16.52	$15.65	$14.96	7
C	Male		Yes	PE6046	$35.39	$33.62	$31.85	$30.44	8
			No	PE6109	$38.59	$36.66	$34.73	$33.19	9
	Female		Yes	PE6110	$35.79	$34.00	$32.21	$30.78	10
			No	PE6111	$27.19	$25.83	$24.47	$23.38	11
F	Male		No	PE6240	$5.28	$5.02	$4.75	$4.54	12
HN			Yes	PE6059	$36.39	$34.57	$32.75	$31.30	13
			No	PE6113	$26.99	$25.64	$24.29	$23.21	14
	Female		Yes	PE6114	$35.59	$33.81	$32.03	$30.61	15
			No	PE6115	$39.39	$37.42	$35.45	$33.88	16

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

CONNECTOR DUST CAPS

Non-Shorting Caps







Connector	Gender	Compatible With	Chain	Model No	1-24	25-49	50-99	100+	ROW
N	Male	50 Ohm	Yes	PE6016	$9.89	$9.40	$8.90	$8.51	17
			No	PE6017	$10.79	$10.25	$9.71	$9.28	18
	Female		Yes	PE6018	$14.59	$13.86	$13.13	$12.55	19
			No	PE6116	$12.59	$11.96	$11.33	$10.83	20
SC	Male		Yes	PE6117	$52.99	$50.34	$47.69	$45.57	21
	Female		Yes	PE6118	$44.19	$41.98	$39.77	$38.00	22
SMA	Male		Yes	PE6019	$22.99	$21.84	$20.69	$19.77	23
			No	PE6024	$5.09	$4.84	$4.58	$4.38	24
	Female		Yes	PE6119	$29.79	$28.30	$26.81	$25.62	25
			No	PE6120	$11.79	$11.20	$10.61	$10.14	26
SMB	Plug		Yes	PE6121	$30.99	$29.44	$27.89	$26.65	27
		75 Ohm	Yes	PE6125	$48.59	$46.16	$43.73	$41.79	28
	Jack	50 Ohm	Yes	PE6122	$26.59	$25.26	$23.93	$22.87	29
SMC	Plug	75 Ohm	Yes	PE6126	$41.99	$39.89	$37.79	$36.11	30
	Jack	50 Ohm	Yes	PE6124	$20.79	$19.75	$18.71	$17.88	31
SSMA	Male		No	PE6020	$23.79	$22.60	$21.41	$20.46	32
TNC			Yes	PE6023	$13.39	$12.72	$12.05	$11.52	33
			No	PE6144	$12.59	$11.96	$11.33	$10.83	34
	Female		Yes	PE6021	$16.39	$15.57	$14.75	$14.10	35

Shorting Caps

Connector	Gender	Compatible With	Chain	Model No	1-24	25-49	50-99	100+	ROW
2.4mm	Male	50 Ohm	Yes	PE6194	$77.99	$74.87	$72.53	$70.97	35
	Female		Yes	PE6195	$92.99	$88.34	$83.69	$79.97	36
			No	PE6193	$84.99	$80.74	$76.49	$73.09	37
BNC	Male		Yes	PE6127	$30.19	$28.68	$27.17	$25.96	38
			No	PE6012	$9.89	$9.40	$8.90	$8.51	39
	Female		Yes	PE6128	$34.39	$32.67	$30.95	$29.58	40
			No	PE6030	$19.59	$18.61	$17.63	$16.85	41
N	Male		Yes	PE6129	$37.59	$35.71	$33.83	$32.33	42
			No	PE6022	$26.79	$25.45	$24.11	$23.04	43
	Female		Yes	PE6130	$60.99	$57.94	$54.89	$52.45	44
			No	PE6031	$13.59	$12.91	$12.23	$11.69	45
SMA	Male		Yes	PE6131	$39.79	$37.80	$35.81	$34.22	46
			No	PE6006	$28.79	$27.35	$25.91	$24.76	47
	Female		Yes	PE6132	$42.19	$40.08	$37.97	$36.28	48
			Yes	PE6251	$31.19	$29.94	$29.01	$28.38	49
			No	PE6007	$30.99	$29.44	$27.89	$26.65	50
TNC	Male		Yes	PE6134	$34.39	$32.67	$30.95	$29.58	51
			No	PE6133	$33.59	$31.91	$30.23	$28.89	52
	Female		Yes	PE6136	$37.99	$36.09	$34.19	$32.67	53
			No	PE6135	$28.79	$27.35	$25.91	$24.76	54

See Our Website For Current Pricing & Real-Time Stock Availability!

COUPLERS AND HYBRIDS

Single Directional

1.85mm Connectors



Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1	2-4	5-9	10+	ROW
1,000-67,000	10	20 Watt	8	PE2CP1127-10	$7,450.00	$7,152.00	$6,854.00	$6,556.00	1
	20			PE2CP1127-20	$7,560.00	$7,257.60	$6,955.20	$6,652.80	

2.4mm Connectors



Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1	2-4	5-9	10+	ROW
2,000-52,000	10	20 Watt	10	PE2CP1134-10	$3,980.00	$3,820.80	$3,661.60	$3,502.40	2
18,000-50,000	20		8	PE2CP1135-20	$3,890.00	$3,734.40	$3,578.80	$3,423.20	3

2.92mm Connectors







Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1	2-4	5-9	10+	ROW
1,000-40,000	10	20 Watt		PE2CP1122-10	$2,620.00	$2,515.20	$2,410.40	$2,305.60	4
	20	30 Watt		PE2CP1122-20	$2,400.00	$2,304.00	$2,208.00	$2,112.00	
	30			PE2CP1122-30	$2,570.00	$2,467.20	$2,364.40	$2,261.60	
2,000-40,000	10		10	PE2CP1133-10	$2,230.00	$2,140.80	$2,051.60	$1,962.40	5
	20			PE2CP1133-20	$1,970.00	$1,891.20	$1,812.40	$1,733.60	
	30			PE2CP1133-30	$2,230.00	$2,140.80	$2,051.60	$1,962.40	
6,000-26,500	10		12	PE2CP1129-10	$1,740.00	$1,670.40	$1,600.80	$1,531.20	6
6,000-40,000			10	PE2CP1124-10	$2,100.00	$2,016.00	$1,932.00	$1,848.00	7
	20			PE2CP1124-20	$2,020.00	$1,939.20	$1,858.40	$1,777.60	
8,000-40,000	10			PE2CP1125-10	$1,950.00	$1,872.00	$1,794.00	$1,716.00	8
	20			PE2CP1125-20	$1,980.00	$1,900.80	$1,821.60	$1,742.40	
	30		10	PE2CP1125-30	$1,980.00	$1,900.80	$1,821.60	$1,742.40	
8,000-43,500	15			PE2CP1125-15	$1,950.00	$1,872.00	$1,794.00	$1,716.00	
18,000-40,000	6		10	PE2CP1126-6	$1,740.00	$1,670.40	$1,600.80	$1,531.20	9
	10		12	PE2CP1126-10	$1,770.00	$1,699.20	$1,628.40	$1,557.60	
	20			PE2CP1126-20	$1,840.00	$1,766.40	$1,692.80	$1,619.20	

4.1/9.5 Mini DIN Connectors



Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1	2-4	5-9	10+	ROW
698-2,700	6	200 Watt	20	PE2CP1059	$595.00	$565.25	$535.50	$511.70	10
	10			PE2CP1063	$595.00	$565.25	$535.50	$511.70	11
	15			PE2CP1067	$685.00	$650.75	$616.50	$589.10	12
	20			PE2CP1071	$595.00	$565.25	$535.50	$511.70	13
	30			PE2CP1075	$595.00	$565.25	$535.50	$511.70	14

4.3-10 Connectors



Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1-4	5-9	10-24	25+	ROW
380-2,700	30	200 Watt	20	PE2CP1076	$650.00	$617.50	$585.00	$559.00	15
698-2,700	6			PE2CP1060	$650.00	$617.50	$585.00	$559.00	16

Single Directional

7/16 DIN Connectors



Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1-4	5-9	10-24	25+	ROW
698-2,700	10	200 Watt	20	PE2CP1062	$735.00	$698.25	$661.50	$632.10	21
	15			PE2CP1066	$735.00	$698.25	$661.50	$632.10	22
	20			PE2CP1070	$660.00	$627.00	$594.00	$567.60	23
	30			PE2CP1074	$660.00	$627.00	$594.00	$567.60	24

N Connectors





Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
500-2,000	30	600 Watt	18	PE2240-30	$1,530.00				25
698-2,700	6	200 Watt	20	PE2CP1057	$595.00				26
	10			PE2CP1061	$660.00				27
	15			PE2CP1065	$660.00				28
800-2,500	6	60 Watt		PE2CP1023-6	$640.00				
	10			PE2CP1023-10	$660.00				
	20			PE2CP1023-20	$645.00				31
	30			PE2CP1023-30	$655.00				
1,000-4,000		600 Watt	15	PE2228A-30	$2,220.00				33
4,000-18,000	10	50 Watt	12	PE2CP1114-10	$735.00				
	20			PE2CP1114-20	$745.00				38

See Web for Volume Pricing

SMA Connectors





Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1-9	10-24	25-49	50+	ROW
500-1,000	10	50 Watt	25	PE2200-10	$499.99	$474.99	$449.99	$429.99	
	20			PE2200-20	$560.00	$532.00	$504.00	$481.60	39
	30			PE2200-30	$560.00	$532.00	$504.00	$481.60	
500-2,000	6		20	PE2CP003-6	$491.99	$467.39	$442.79	$423.11	40
			23	PE2208-6	$665.00	$631.75	$598.50	$571.90	41
	10		20	PE2CP003-10	$345.99	$328.69	$311.39	$297.55	42
			23	PE2208-10	$655.00	$622.25	$589.50	$563.30	43
	20		20	PE2CP003-20	$367.99	$349.59	$331.19	$316.47	44
			23	PE2208-20	$675.00	$641.25	$607.50	$580.50	45
500-3,000	10		18	PE2242-10	$351.99	$334.39	$316.79	$302.71	46
	20			PE2242-20	$351.99	$334.39	$316.79	$302.71	
				PE2242A-20	$351.99	$334.39	$316.79	$302.71	47
	30			PE2242-30	$351.99	$334.39	$316.79	$302.71	48

SMA Connectors






Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
500-18,000	10	30 Watt		PE2243-10	$1,800.00		
	16			PE2243-16	$1,780.00		49
	20			PE2243-20	$1,870.00		
	30			PE2243-30	$1,800.00		
600-4,000	10	50 Watt	18	PE2213-10	$945.00		50
700-2,700	6		20	PE2CP002-6	$327.99		
	10			PE2CP002-10	$321.99		51
	20			PE2CP002-20	$315.99		
800-2,200	10			PE2CP025-10	$273.99		52
800-2,500	6			PE2CP1024-6	$645.00		53
	10			PE2CP1025-10	$660.00		54
	20			PE2CP1025-20	$590.00		
	30			PE2CP1024-30	$645.00		55
1,000-2,000	10		25	PE2201-10	$467.99		56
	20			PE2CP1108	$215.99		57
	30			PE2201-30	$465.99		58
1,000-4,000	6		20	PE2CP005-6	$271.99		59
			23	PE2209-6	$645.00		60
	10		20	PE2CP005-10	$263.99		61
				PE2CP1102	$233.99	See Web for Volume Pricing	62
	20			PE2CP005-20	$279.99		63
			23	PE2209-20	$700.00		64
2,000-4,000	6		22	PE2202-6	$473.99		65
	30			PE2202-30	$433.99		
2,000-8,000	6		20	PE2CP004-6	$353.99		66
				PE2210-6	$615.00		67
	10			PE2CP004-10	$379.99		68
				PE2210-10	$580.00		69
	20			PE2CP004-20	$371.99		70
				PE2210-20	$640.00		71
2,000-18,000	6	4 Watt	12	PE2215-6	$2,330.00		72
	10	25 Watt		PE2215-10	$2,560.00		
		50 Watt		PE2CP000-10	$780.00		73
				PE2CP1103	$560.00		74
	20			PE2CP000-20	$825.00		75
	30		10	PE2CP000-30	$800.00		
2,000-18,400	20	25 Watt	12	PE2215-20	$2,190.00		76
2,600-5,200	10	50 Watt	20	PE2203-10	$660.00		77
	20			PE2CP1109	$227.99		78
				PE2203-20	$675.00		
	30			PE2203-30	$690.00		79
4,000-8,000	6			PE2204-6	$443.99		
	10			PE2204-10	$427.99		
	20			PE2204-20	$459.99		80
	30			PE2204-30	$481.99		
4,000-12,400	6		17	PE2211-6	$685.00		
	10			PE2211-10	$640.00		81
	20			PE2211-20	$660.00	See Web for Volume Pricing	
4,000-18,000	6		12	PE2CP1100	$479.99		82
	10			PE2CP1104	$479.99		83
	20			PE2CP1110	$473.99		84
6,000-18,000	10		10	PE2CP001-10	$605.00		
	20		12	PE2CP001-20	$670.00		85
6,000-26,500	10	30 Watt		PE2CP1120-10	$1,310.00		
	30		13	PE2CP1120-30	$1,240.00		86
6,000-26,600	20			PE2CP1120-20	$1,310.00		
7,000-12,400	6	50 Watt	17	PE2CP1101	$379.99		87
	10			PE2CP1105	$383.99		88
	20			PE2205-20	$695.00		
	30			PE2205-30	$640.00		89
7,000-16,000			12	PE2CP1112	$431.99		90
7,000-18,000	10		15	PE2CP1106	$393.99		91
7,500-16,000	6		12	PE2206-6	$595.00		92
	10			PE2CP1107	$369.99		93
12,400-18,000	6	4 Watt	15	PE2207-6	$705.00		94
	10	50 Watt		PE2207-10	$625.00		
	20			PE2CP1111	$427.99		95
	30			PE2207-30	$630.00		96
18,000-26,000		30 Watt	13	PE2CP1121-30	$1,090.00		97

Dual Directional

N Connectors





Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1	2-4	5-9	10+	ROW
2-30	50	2500 Watt	22	PE2CP1000	$3,810.00	$3,657.60	$3,505.20	$3,352.80	98
20-500		500 Watt	20	PE2CP1002	$2,210.00	$2,121.60	$2,033.20	$1,944.80	99
		1000 Watt		PE2CP1003	$2,950.00	$2,832.00	$2,714.00	$2,596.00	1
20-1,000		500 Watt		PE2CP1005	$2,200.00	$2,112.00	$2,024.00	$1,936.00	2
80-1,000		200 Watt		PE2CP1021	$1,800.00	$1,728.00	$1,656.00	$1,584.00	3
		500 Watt		PE2CP1007	$2,150.00	$2,064.00	$1,978.00	$1,892.00	4
		1000 Watt		PE2CP1008	$3,130.00	$3,004.80	$2,879.60	$2,754.40	5
100-500	40	500 Watt		PE2CP1010	$2,020.00	$1,939.20	$1,858.40	$1,777.60	6
500-2,500		200 Watt	18	PE2CP1011	$1,300.00	$1,248.00	$1,196.00	$1,144.00	8
		500 Watt	20	PE2CP1012	$2,080.00	$1,996.80	$1,913.60	$1,830.40	9
500-3,000		200 Watt	18	PE2CP1013	$2,240.00	$2,150.40	$2,060.80	$1,971.20	10
800-2,500		500 Watt	20	PE2CP1015	$2,200.00	$2,112.00	$2,024.00	$1,936.00	11
800-4,200		200 Watt		PE2CP1016	$2,610.00	$2,505.60	$2,401.20	$2,296.80	12
2,000-6,000	20		15	PE2CP1019	$1,790.00	$1,718.40	$1,646.80	$1,575.20	13

SC Connectors




Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1	2-4	5-9	10+	ROW
20-1,000	50	1000 Watt	20	PE2CP1006	$3,420.00	$3,283.20	$3,146.40	$3,009.60	14
800-4,200	40	600 Watt	18	PE2CP1017	$3,510.00	$3,369.60	$3,229.20	$3,088.80	15

SMA Connectors






Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
20-520	50	200 Watt	20	PE2CP1001	$1,420.00				16
20-1,000				PE2CP1004	$1,780.00				17
100-500	40			PE2CP1009	$1,630.00				18
500-1,000	10	10 Watt	22	PE2217-10	$950.00				19
	20	50 Watt		PE2217-20	$965.00				
	30			PE2217-30	$930.00				
800-2,500	40	200 Watt	20	PE2CP1014	$1,350.00				20
1,000-2,000	10	10 Watt	22	PE2218-10	$930.00				21
	20	50 Watt		PE2218-20	$930.00				
	30			PE2218-30	$940.00				
2,000-4,000	20		20	PE2219-20	$1,070.00				22
2,000-6,000		100 Watt	16	PE2CP1018	$1,340.00				23
2,000-8,000		50 Watt	20	PE2CP1113	$780.00				24
2,600-5,200	10	10 Watt	18	PE2220-10	$975.00				25
	20	50 Watt		PE2220-20	$860.00				
4,000-8,000	10	10 Watt		PE2221-10	$945.00				26
7,000-12,400	30	50 Watt	16	PE2222-30	$930.00				27
8,000-16,000	10	10 Watt	15	PE2223-10	$930.00				28
	20	50 Watt		PE2223-20	$1,050.00				
	30			PE2223-30	$965.00				
12,400-18,000	20			PE2224-20	$980.00				29

See Web for Volume Pricing

90 Degree Hybrids

2.92mm Connectors



Frequency Range (MHz.)	Maximum Power	Minimum Isolation (dB)	Model No	1-4	5-9	10-24	25+	ROW
2,000-40,000	20 Watt	10	PE2CP1150	$2,460.00	$2,337.00	$2,214.00	$2,115.60	30
5,000-26,500		14	PE2CP1147	$1,250.00	$1,187.50	$1,125.00	$1,075.00	31
8,000-43,500		12	PE2CP1149	$1,850.00	$1,757.50	$1,665.00	$1,591.00	32
10,000-26,500		15	PE2CP1146	$1,190.00	$1,130.50	$1,071.00	$1,023.40	33
20,000-40,000		12	PE2CP1148	$1,850.00	$1,757.50	$1,665.00	$1,591.00	34

Pin Connectors






Frequency Range (MHz.)	Maximum Power	Minimum Isolation (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
20-1,000	50 Watt	16	PE2CP1026	$950.00		See Web for Volume Pricing		35
	150 Watt		PE2CP1027	$1,060.00				36
80-1,000	250 Watt		PE2CP1028	$745.00				37
100-500	150 Watt		PE2CP1029	$347.99				38
130-180	200 Watt	20	PE2CP1032	$109.99				39
225-400	250 Watt	20	PE2CP1034	$133.99				41
225-450	400 Watt		PE2CP1035	$179.99				42
	800 Watt		PE2CP1036	$457.99				43
400-1,000	200 Watt	19	PE2CP1037	$92.99				44
	400 Watt	20	PE2CP1038	$137.99				45
500-2,500	150 Watt	18	PE2CP1040	$213.99				47
	300 Watt		PE2CP1042	$471.99				49
500-3,000	125 Watt	18	PE2CP1043	$217.99				50
	200 Watt	17	PE2CP1044	$395.99				51
800-1,600		20	PE2CP1045	$105.99				52
960-1,220	125 Watt	20	PE2CP1048	$96.99				55
1,000-2,000	200 Watt		PE2CP1049	$95.99				56
	1000 Watt	18	PE2CP1051	$535.00				58
1,000-3,000	150 Watt		PE2CP1052	$113.99				59
1,000-4,200	80 Watt	18	PE2CP1054	$185.99				61
2,000-4,000	100 Watt		PE2CP1055	$96.99				62
2,000-6,000			PE2CP1056	$95.99				63

SMA Connectors





Frequency Range (MHz.)	Maximum Power	Minimum Isolation (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
500-1,000	50 Watt	22	PE2CP011	$291.99		See Web for Volume Pricing		64
			PE2CP1140	$615.00				65
	100 Watt	28	PE2050	$650.00				66
800-3,000	50 Watt	20	PE2CP021	$433.99				67
1,000-2,000		22	PE2CP013	$291.99				68
1,000-18,000		15	PE2CP1144	$785.00				69
1,400-2,500		23	PE2CP1145	$695.00				70
2,000-4,000		22	PE2CP017	$291.99				71
			PE2052	$555.00				72
2,000-8,000	30 Watt	17	PE2058	$610.00				73
2,000-18,000	50 Watt	15	PE2CP023	$1,320.00				74
4,000-8,000		18	PE2CP019	$291.99				75
4,000-12,400	100 Watt		PE2059	$910.00				76
4,000-18,000	50 Watt	16	PE2CP1143	$685.00				77
5,000-10,000		20	PE2CP1141	$615.00				78
6,000-12,400	100 Watt	17	PE2055	$630.00				79

SMA Connectors





Frequency Range (MHz.)	Maximum Power	Minimum Isolation (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
6,000-18,000	30 Watt	16	PE2CP1142	$735.00		See Web for Volume Pricing		80
7,000-18,000		18	PE2CP1022	$770.00				81
7,500-16,000	100 Watt		PE2056A	$655.00				82
12,000-18,000	40 Watt	15	PE2057	$590.00				83

180 Degree Hybrids

2.92mm Connectors



Frequency Range (MHz.)	Maximum Power	Minimum Isolation (dB)	Model No	1-4	5-9	10-24	25+	ROW
26,500-40,000	20 Watt	15	PE2CP1161	$2,570.00	$2,441.50	$2,313.00	$2,210.20	84

SMA Connectors





Frequency Range (MHz.)	Maximum Power	Minimum Isolation (dB)	Model No	1-4	5-9	10-24	25+	ROW
500-1,000	50 Watt	22	PE2CP1151	$850.00	$807.50	$765.00	$731.00	85
1,000-2,000			PE2CP1152	$865.00	$821.75	$778.50	$743.90	86
1,300-2,600	100 Watt	20	PE2CP1153	$850.00	$807.50	$765.00	$731.00	87
1,400-6,000	30 Watt	22	PE2CP1154	$1,660.00	$1,577.00	$1,494.00	$1,427.60	88
2,000-4,000	50 Watt	20	PE2CP1155	$850.00	$807.50	$765.00	$731.00	89
2,000-8,000	30 Watt		PE2CP1157	$1,130.00	$1,073.50	$1,017.00	$971.80	90
2,000-18,000	50 Watt	16	PE2CP1158	$1,730.00	$1,643.50	$1,557.00	$1,487.80	91
4,000-8,000	80 Watt	18	PE2CP1159	$945.00	$897.75	$850.50	$812.70	92
4,000-18,000	50 Watt		PE2CP1160	$1,290.00	$1,225.50	$1,161.00	$1,109.40	93

RF DIPLEXERS

75 Ohm Diplexer F Female with 5 MHz to 390 MHz Low Pass and 650 MHz to 1,000 MHz High Pass PE8DP1001

- 5 - 1000 MHz
- 75 Ohms Impedance
- Typical Return loss 18 dB
- Bidirectional design
- EN 50083-2 Class A Standard



In-stock and available to ship today!

NEW

Low Pass Harmonic Filters: PEHFL0000 - PEHFL0001

- Passband frequency: DC - 6000Hz
- 50 Ohms impedance
- Broadband design: C, L & S Band
- RF input power passband: 50 W
- VSWR: 1.5:1



In-stock and available to ship today!

N Connectors

Band Pass




Bandpass Frequency (MHz)	Application	Rejection (MHz)	Max. Insertion Loss (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
125 - 250		5%	5	PE8728	$2,790.00	See Web for Volume Pricing	94
250 - 500				PE8729	$2,850.00		95
500 - 1 GHz				PE8730	$3,060.00		96
750 - 1.5 GHz				PE8731	$3,020.00		97
1 GHz - 2 GHz				PE8732	$2,830.00		98
1.5 GHz - 3 GHz				PE8733	$2,730.00		99

Band Reject




Bandpass Frequency (MHz)	Application	Rejection (MHz)	Max. Insertion Loss (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
100 - 200		1%	3	PE8734	$3,100.00	See Web for Volume Pricing	1
200 - 400				PE8735	$2,790.00		2
250 - 500				PE8736	$3,300.00		3
1 GHz - 2 GHz				PE8738	$2,990.00		4





Bandpass Frequency (MHz)	Application	Rejection (MHz)	Max. Insertion Loss (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
160 - 163	PTC	60 dB at 110 60 dB at 220		PE73SP1045	$283.99	See Web for Volume Pricing	5
	PTC			PE73SP1046	$297.99		6
217 - 223	PTC	60 dB at 160 45 dB at 450		PE73SP1043	$283.99		7
	PTC			PE73SP1044	$283.99		8
450 - 460	PTC	60 dB at 250 60 dB at 650		PE73SP1047	$297.99		9

SMA Connectors

Bandpass Filters





Bandpass Frequency (MHz)	Application	Rejection (MHz)	Max. Insertion Loss (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
824 - 849	GSM	50 dB at 736.5 50 dB at 936.5	2	PE8705	$605.00	See Web for Volume Pricing	10
869 - 894	GSM	50 dB at 781.5 50 dB at 981.5		PE8706	$625.00		11
902 - 928	ISM, RFID	50 dB at 815 50 dB at 1,015		PE8700	$630.00		12
1,000 - 2,000		55 dB at 650 55 dB at 3,000		PE87FL1012	$540.00		13
1,217 - 1,237	GPS L2	50 dB at 1,127 50 dB at 1,327	1	PE8704	$680.00		14
1,565 - 1,585	GPS L1	50 dB at 1,475 50 dB at 1,675	2	PE8703	$565.00		15
1,710 - 1,770	UMTS/AWS	50 dB at 1,490 50 dB at 1,990		PE8710	$625.00		16
1,850 - 1,910	PCS	50 dB at 1,630 50 dB at 2,130		PE8707	$630.00		17
1,920 - 1,980	UMTS	50 dB at 1,700 50 dB at 2,200		PE8709	$660.00		18
1,930 - 1,990	PCS	50 dB at 1,710 50 dB at 2,210		PE8708	$745.00		19
2,000 - 4,000		55 dB at 1,300 55 dB at 6,000		PE87FL1013	$560.00		20
2,110 - 2,170	UMTS/AWS	50 dB at 1,890 50 dB at 2,390		PE8711	$925.00		21
2,400 - 2,500	ISM, WiFi, Bluetooth, Zigbee	50 dB at 2,050 50 dB at 2,850	1	PE8701	$645.00		22
2,500 - 2,700	WIMAX	50 dB at 1,700 50 dB at 3,500	2	PE8712	$720.00		23
3,300 - 3,700	WiMAX	50 dB at 1,600 50 dB at 5,400		PE8713	$605.00		24
4,400 - 4,950	P2P, Public Safety	30 dB at 5,250 30 dB at 5,850	1	PE8739	$463.99		25
4,900 - 5,900	WiMAX	50 dB at 400 50 dB at 10,400	2	PE8714	$595.00		26
5,250 - 5,850	P2P, Public Safety	30 dB at 4,400 30 dB at 4,950	1	PE8740	$433.99		27
5,725 - 5,875	ISM, WiFi	50 dB at 5,200 50 dB at 6,400		PE8702	$600.00		28
7,250 - 7,750	VSAT	30 dB at 7,900 30 dB at 8,400	2	PE8741	$499.99		29
7,900 - 8,400	VSAT	30 dB at 7,250 30 dB at 7,750		PE8742	$499.99		30
9,900 - 10,800		50 dB at 8,350 50 dB at 12,350	1	PE87FL1000	$640.00		31
10,550 - 11,800		50 dB at 8,425 50 dB at 13,925		PE87FL1001	$660.00		32
10,700 - 12,200		50 dB at 8,450 50 dB at 14,450		PE87FL1003	$640.00		33
11,700 - 12,800		50 dB at 9,750 50 dB at 14,750		PE87FL1002	$660.00		34
12,200 - 12,700		50 dB at 11,450 50 dB at 13,450	2	PE87FL1004	$630.00		35
14,000 - 14,800		50 dB at 12,850 50 dB at 15,950		PE87FL1005	$595.00		36
17,200 - 18,200		35 dB at 16,200 35 dB at 19,200		PE87FL1008	$670.00		37
17,200 - 21,200		50 dB at 13,450 50 dB at 24,950	1	PE87FL1007	$530.00		38
17,300 - 18,100		50 dB at 16,200 50 dB at 19,200	2	PE87FL1006	$640.00		39
17,700 - 21,200	VSAT	50 dB at 16,000 50 dB at 24,000		PE8743	$610.00		40
18,200 - 19,200		35 dB at 17,200 35 dB at 20,200		PE87FL1009	$595.00		41
19,200 - 20,200		35 dB at 18,200 35 dB at 21,200		PE87FL1010	$605.00		42
20,200 - 21,200		35 dB at 19,200 35 dB at 22,200		PE87FL1011	$560.00		43
27,500 - 31,000	VSAT	50 dB at 25,000 50 dB at 32,750	3	PE8747	$555.00		44

SMA Connectors

Highpass Filters




Bandpass Frequency (MHz)	Rejection (MHz)	Max. Insertion Loss (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
100 - 300	60 dB at 15	1	PE8717	$477.99	See Web for Volume Pricing	45
100 - 750	60 dB at 50		PE8716	$765.00		46
100 - 2,500	60 dB at 500		PE8715	$477.99		47
300 - 1,000	60 dB at 150		PE8718	$455.99		48
1,000 - 13,000	40 dB at 0	2	PE87FL1018	$1,210.00		49
2,000 - 18,000			PE87FL1019	$965.00		50

Lowpass Filters




Bandpass Frequency (MHz)	Rejection (MHz)	Max. Insertion Loss (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
DC - 30	60 dB at 60	1	PE8723	$431.99	See Web for Volume Pricing	51
DC - 100	60 dB at 200		PE8719	$411.99		52
DC - 225	60 dB at 450		PE8722	$395.99		53
DC - 300	60 dB at 600		PE8724	$660.00		54
DC - 400	60 dB at 800		PE8726	$303.99		55
DC - 700	60 dB at 1,400		PE8727	$437.99		56
DC - 1,000	60 dB at 2,000		PE8720	$399.99		57
DC - 2,000	60 dB at 4,000		PE8721	$397.99		58
DC - 3,000	60 dB at 6,000		PE8725	$467.99		59
DC - 4,400	50 dB at 12,000	2	PE87FL1014	$545.00		60
DC - 7,000	50 dB at 15,000		PE87FL1015	$540.00		61
DC - 9,500	50 dB at 18,000		PE87FL1016	$575.00		62
DC - 11,000			PE87FL1017	$530.00		63

FREQUENCY DIVIDERS





Input Frequency (GHz)	Divide-By Prescaler	CW Input Power (CW) (dBm)	Typ Power Out (dBm)	Phase Noise @100 kHz (dBc/Hz)	DC Bias (Volts/mA)	Model No	1	2-4	5-9	10+	ROW
0.1 - 7	3	-12	-1	-150	+12 / 70	PE88D3000	$1,170.00	$1,099.80	$1,041.30	$994.50	64
	5				+12 / 80	PE88D25000	$1,110.00	$1,043.40	$987.90	$943.50	65
	15				+12 / 150	PE88D15000	$1,220.00	$1,146.80	$1,085.80	$1,037.00	66
0.1 - 12	8				+12 / 75	PE88D8003	$1,230.00	$1,156.20	$1,094.70	$1,045.50	67
	24		-1	-147	+12 / 140	PE88D24000	$1,420.00	$1,334.80	$1,263.80	$1,207.00	68
	40				+12 / 150	PE88D40000	$1,490.00	$1,400.60	$1,326.10	$1,266.50	69
0.1 - 12.5	10			-144	+12 / 200	PE88D1001	$1,500.00	$1,410.00	$1,335.00	$1,275.00	70
0.1 - 13	4		5	-151	+12 / 120	PE88D4003	$1,330.00	$1,250.20	$1,183.70	$1,130.50	71
	12			-145	+12 / 185	PE88D12000	$1,440.00	$1,353.60	$1,281.60	$1,224.00	72
	20		-1		+12 / 195	PE88D20000	$1,420.00	$1,334.80	$1,263.80	$1,207.00	73
0.1 - 15	5		5	-153	+5 / 205	PE88D5001	$1,870.00	$1,757.80	$1,664.30	$1,589.50	74
	6				+5 / 205	PE88D6000	$1,840.00	$1,729.60	$1,637.60	$1,564.00	75
	7				+5 / 205	PE88D7000	$1,840.00	$1,729.60	$1,637.60	$1,564.00	76
	9				+5 / 205	PE88D9000	$1,840.00	$1,729.60	$1,637.60	$1,564.00	77
0.1 - 20	2				+5 / 160	PE88D2002	$1,940.00	$1,823.60	$1,726.60	$1,649.00	78
	4				+5 / 170	PE88D4002	$1,870.00	$1,757.80	$1,664.30	$1,589.50	79
	8				+5 / 175	PE88D8002	$1,840.00	$1,729.60	$1,637.60	$1,564.00	80
0.2 - 6	10		-2	-144	+12 / 100	PE88D1002	$1,010.00	$949.40	$898.90	$858.50	81
	20		2		+12 / 95	PE88D20001	$1,010.00	$949.40	$898.90	$858.50	82
0.4 - 4	16				+12 / 70	PE88D16000	$880.00	$827.20	$783.20	$748.00	83
	32		1		+12 / 70	PE88D32000	$895.00	$841.30	$796.55	$760.75	84
0.5 - 8	5	-20	-1		+5 / 80	PE88D5000	$3,360.00	$3,225.60	$3,091.20	$2,956.80	85
0.5 - 18	2	-15	-4	-147	+12 / 85	PE88D2001	$1,680.00	$1,579.20	$1,495.20	$1,428.00	86
	4	-20			+5 / 93	PE88D4000	$4,790.00	$4,598.40	$4,406.80	$4,215.20	87
		-15		-147	+12 / 110	PE88D4001	$1,680.00	$1,579.20	$1,495.20	$1,428.00	88
	8				+12 / 110	PE88D8001	$1,780.00	$1,673.20	$1,584.20	$1,513.00	89
	10	-20	-1		+5 / 152	PE88D1000	$5,230.00	$4,916.20	$4,654.70	$4,445.50	90

MIXERS

Double Balanced






RF Range (GHz)	LO Range (GHz)	IF Range (GHz)	LO Power (dBm)	Conv. Loss (dB)	Connector	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
0.5 MHz- 500 MHz	0.5 MHz- 500 MHz	DC - 500 MHz	10	6.8	SMA	PE86X1013	$393.99		91
1 MHz- 2.7	1 MHz- 2.7	1 MHz - 2	10	7	SMA	PE86X1020	$505.00		92
			17			PE86X1021	$615.00		93
5 MHz- 1	5 MHz- 1	DC - 1	7	7	SMA	PE86X1014	$393.99		94
			13			PE86X1016	$373.99		95
5 MHz- 1.5	5 MHz- 1.5	DC - 1	7	7.5	SMA	PE86X1018	$393.99		96
5 MHz- 3.5	5 MHz- 3.5	5 MHz - 2.5	13	8	SMA	PE86X1022	$455.99		97
5 MHz- 4.2	5 MHz- 4.2	5 MHz - 3.5	13	9.8	SMA	PE86X1023	$505.00		98
10 MHz- 1	10 MHz- 1	DC - 800 MHz	4	7.2	SMA	PE86X1015	$393.99		99
10 MHz- 1.2	10 MHz- 1.2	DC - 1.2	13	8	SMA	PE86X1017	$395.99		1
40 MHz- 2.5	40 MHz- 2.5	DC - 1	13	8	SMA	PE86X1019	$550.00		2
800 MHz- 4.2	800 MHz- 4.2	DC - 800 MHz	13	9	SMA	PE86X1024	$439.99		3
2 - 8	2 - 8	DC - 1.5	10	5.5	SMA	PE8650	$855.00		4
2 - 18	2 - 18	DC - 600 MHz	10	6.5	SMA	PE8652	$1,110.00		5
2.25 - 18	2.25 - 18	DC - 3	13	11	SMA	PE86X1026	$1,410.00		6
2.5 - 6	2.5 - 6	DC - 1.5	17	8.7	SMA	PE86X1025	$570.00		7
3 - 10	3 - 10	DC - 4	17	9	SMA	PE86X1027	$1,410.00		8
5 - 18	5 - 18	DC - 4	10	6.2	SMA	PE8653	$1,220.00		9
5 - 20	5 - 20	DC - 3	20	10	SMA	PE86X1006	$1,710.00		10
						PE86X1008	$1,710.00		11
6 - 18	6 - 18	DC - 3	6	7.5	SMA	PE86X1007	$1,800.00		12
6 - 26	6 - 26	DC - 8	13	10	SMA	PE86X1028	$1,540.00		13
7 - 14	7 - 14	DC - 5	13		SMA	PE86X1003	$5,610.00		14
7 - 34	7 - 34	DC - 8	15	11	2.92mm	PE86X1029	$1,610.00		15
7 - 43	7 - 43	DC - 10	13	9	2.92mm	PE86X1009	$3,520.00		16
16 - 30	16 - 30	DC - 8	13	9	2.92mm	PE86X1030	$1,710.00		18
16 - 32	16 - 32	DC - 8	13		2.92mm	PE86X1000	$4,150.00		19
24 - 32	24 - 32	DC - 8	13	10.5	2.92mm	PE86X1031	$1,720.00		20
24 - 38	24 - 38	DC - 8	13	9	2.92mm	PE86X1001	$5,590.00		21
24 - 40	24 - 40	DC - 18	13	8	2.92mm	PE86X1010	$3,290.00		22

See Web for Volume Pricing

IQ



RF Range (GHz)	LO Range (GHz)	IF Range (GHz)	LO Power (dBm)	Conv. Loss (dB)	Connector	Model No	1	2-4	5-9	10+	ROW
4 - 8.5	4 - 8.5	DC - 3.5	15		SMA	PE86X9000	$3,800.00	$3,667.00	$3,534.00	$3,420.00	23
6 - 10	6 - 10	DC - 3.5	19	7.5	SMA	PE86X9001	$3,800.00	$3,648.00	$3,496.00	$3,344.00	24
11 - 16	11 - 16	DC - 3.5	19	9	SMA	PE86X9003	$4,560.00	$4,377.60	$4,195.20	$4,012.80	25
15 - 23	15 - 23	DC - 3.5	17	8	SMA	PE86X9004	$4,940.00	$4,742.40	$4,544.80	$4,347.20	26
20 - 31	20 - 31	DC - 4.5	17	10	2.92mm	PE86X9005	$6,280.00	$6,028.80	$5,777.60	$5,526.40	27
30 - 38	30 - 38	DC - 3.5	17		2.92mm	PE86X9006	$6,320.00	$6,067.20	$5,814.40	$5,561.60	28

Triple Balanced



RF Range (GHz)	LO Range (GHz)	IF Range (GHz)	LO Power (dBm)	Conv. Loss (dB)	Connector	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
2 - 18	2 - 18	1 - 6		8	SMA	PE86X1032	$2,540.00		29
6 - 18	6 - 18	1.5 - 8	10	7	SMA	PE8654	$1,220.00		30

MODULATOR

BiPhase





Freq. Band (GHz.)	Insertion Loss (dB)	Switching Speed (nsec)	Phase State (On/Off)	VSWR	RF Input Power (CW) (dBm)	Max Peak RF Input Power (1usec	RF Conn.	Model No	1	2-4	5-9	10+	ROW
0.5 to 1	2.5	10	0°/180°	2:1	+20	0.5	SMA Female	PE86GM2000	$4,250.00	$4,101.25	$3,952.50	$3,825.00	31
1 to 2	3	30						PE86GM2001	$4,540.00	$4,381.10	$4,222.20	$4,086.00	32
2 to 4	2.5	75		1.5:1				PE86GM2002	$4,820.00	$4,651.30	$4,482.60	$4,338.00	33
2 to 6	1.7	50		1.8:1	+27			PE86GM2003	$5,110.00	$4,931.15	$4,752.30	$4,599.00	34
4 to 8	2.5	30		2:1	+20			PE86GM2004	$5,390.00	$5,201.35	$5,012.70	$4,851.00	35
6 to 12		15						PE86GM2005	$5,680.00	$5,481.20	$5,282.40	$5,112.00	36
8 to 18	3	75						PE86GM2006	$5,960.00	$5,751.40	$5,542.80	$5,364.00	37
2 to 18	3.5	35		1.7:1				PE86GM2007	$7,100.00	$6,851.50	$6,603.00	$6,390.00	38
26.5 to 40	5.5	50		2:1			2.92mm	PE86GM2008	$8,520.00	$8,221.80	$7,923.60	$7,668.00	39

FREQUENCY MULTIPLIERS

Active




Type	Input Freq. (GHz.)	Output Freq. (GHz.)	CW Input Power (dBm)	Fund. Iso. Typ (dB)	Conversion Gain (dB)	DC Voltage	Female In/Out Conn.	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
Triplers	250 MHz - 350 MHz	750 MHz - 1.05	-3	40	7	12	SMA	PE88X2015	$805.00	See Web for Volume Pricing	40
	320 MHz - 450 MHz	960 MHz - 1.35	-3	30	6			PE88X2016	$805.00		41
	450 MHz - 600 MHz	1.35 - 1.8	-3	35	9			PE88X2017	$805.00		42
	600 MHz - 750 MHz	1.8 - 2.25	-3	30	4			PE88X2018	$805.00		43
	700 MHz - 1000 MHz	2.1 - 3	0	25	12			PE88X2019	$805.00		44
	950 MHz - 1.5	2.85 - 4.5	0	20	9			PE88X2020	$805.00		45
	9 - 14.5	18 - 29	3	20	13	5	2.92mm	PE88X2000*	$5,680.00		47
	12 - 16.5	24 - 33	3	20	14			PE88X2001*	$5,590.00		48
	16 - 23	32 - 46	3	20	10			PE88X2002*	$6,240.00		49

*Field Replaceable Connectors

Passive Doublers




Input Freq. (GHz.)	Output Freq. (GHz.)	Input Drive Power (dBm)	Conversion Loss (dB)	Fund. Iso. Typ (dB)	Female In/Out Conn.	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
10 MHz - 1000 MHz	20 MHz - 2	12	12	35	SMA	PE88X2010	$600.00	See Web for Volume Pricing	50
900 MHz - 1.8	1.8 - 4	12	14			PE88X2011	$600.00		51

*Field Replaceable Connectors

Passive Doublers




Input Freq. (GHz.)	Output Freq. (GHz.)	Input Drive Power (dBm)	Conversion Loss (dB)	Fund. Iso. Typ (dB)	Female In/Out Conn.	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
1.25 - 3	2.5 - 6	12	15	25		PE88X2012	$600.00		See Web for Volume Pricing		52
1.5 - 5	3 - 10	13	8.5	25		PE8600	$865.00				53
2 - 4	4 - 8	12	14	25		PE88X2013	$600.00				54
2 - 6	4 - 12	13	11	25		PE8601	$910.00				55
4 - 8	8 - 16	12	17	25		PE88X2014	$600.00				56
4 - 9	8 - 18	13	10	25		PE8602	$920.00				57
9 - 13	18 - 26					PE8603	$920.00				58

*Field Replaceable Connectors

LIMITERS

High Rel






Frequency Range (GHz.)	Insertion Loss Max. (dB)	Input VSWR Typ.	Leakage Power Max. (dBm)	Recovery Time Typ. (ns)	Input Power (CW) Max. (W)	Peak Power Max. (W)	Limiting Threshold Typ. (dBm)	Model No	1	2-4	5-9	10+	ROW
20 MHz - 4	0.8	1.8:1	13	15,000	2	100	10	PE80L2003	$1,500.00	$1,440.00	$1,380.00	$1,320.00	59
500 MHz - 18	1.5	1.5:1	10	10	1			PE80L1000	$4,910.00	$4,713.60	$4,517.20	$4,320.80	60
	1.6	1.8:1	14		2	20	14	PE80L2009	$2,150.00	$2,021.00	$1,913.50	$1,827.50	61
	2	1.8:1	18	15,000	5	100		PE80L2005	$2,140.00	$2,054.40	$1,968.80	$1,883.20	62
2 - 8	1	2:1	13	40				PE80L1001	$5,750.00	$5,520.00	$5,290.00	$5,060.00	63
2 - 18	2	2:1	14	100	1	200	6	PE80L2001	$5,660.00	$5,433.60	$5,207.20	$4,980.80	64
		2:1		100				PE80L3000	$5,570.00	$5,347.20	$5,124.40	$4,901.60	65
	2.5	2:1		15,000	5	100		PE80L2006	$1,830.00	$1,756.80	$1,683.60	$1,610.40	66
6 - 18			15	12	10			PE80L2000	$4,370.00	$4,195.20	$4,020.40	$3,845.60	67
8 - 12	1.2	1.8:1	18	15,000	3		15	PE80L2004	$1,680.00	$1,612.80	$1,545.60	$1,478.40	68
12 - 18	1.5	1.5:1	10	10	1		1	PE80L4000	$5,980.00	$5,740.80	$5,501.60	$5,262.40	69
18 - 40	4	2.1:1	12	10		20	5	PE80L2002	$6,050.00	$5,808.00	$5,566.00	$5,324.00	70
	4.5	3:1	13	15,000		100	6	PE80L2007	$2,540.00	$2,438.40	$2,336.80	$2,235.20	71
26.5 - 40	3	2:1		15,000				PE80L2008	$2,160.00	$2,073.60	$1,987.20	$1,900.80	72

PIN-PIN





Frequency Range (GHz.)	Limiting Threshold Typ. (dBm)	Leakage @1W CW Input Max. (dBm)	Insertion Loss Max. (dBm)	Input VSWR Typ.	In Power (CW) Max. (W)	In Peak Power Max. (W)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
500 MHz - 1	12	20	0.4	1.4:1	1	100	PE8017	$580.00		See Web for Volume Pricing		73
500 MHz - 2		19	0.5	1.4:1			PE8018	$605.00				74
1 - 2	9	19	0.2	1.2:1			PE8019	$640.00				75
2 - 4	12	19	0.8	1.5:1			PE8020	$565.00				76
2 - 8	9	16	1.2	1.6:1			PE8021	$725.00				77
2 - 18	12	18	2.5	2.2:1			PE8022	$730.00				78
4 - 8	9	16	1	1.3:1			PE8023	$675.00				79
6 - 18	12	16	2.2	2:1			PE8024	$705.00				80
7 - 12		16	1.8	1.8:1			PE8025	$675.00				81
8 - 16		16	2	2:1			PE8026	$640.00				82
11 - 18	9	16		2:1			PE8027	$770.00				83

PIN-Schottky




Frequency Range (GHz.)	Limiting Threshold Typ. (dBm)	Leakage @1W CW Input Max. (dBm)	Insertion Loss Max. (dBm)	Input VSWR Typ.	In Power (CW) Max. (W)	In Peak Power Max. (W)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
500 MHz - 1	12	14	0.5	1.4:1	1	100	PE8028	$560.00		See Web for Volume Pricing		84
500 MHz - 2	9	14	0.4	1.25:1		200	PE8029	$615.00				85
1 - 2	4	14	0.6	1.4:1		100	PE8030	$755.00				86
2 - 4		14	0.8	1.5:1		200	PE8031	$710.00				87
2 - 8	9	14	1.2	1.4:1			PE8032	$645.00				88
2 - 18	4	18	2.5	2.2:1		100	PE8033	$715.00				89
4 - 8		13	1.4	1.5:1			PE8034	$735.00				90
6 - 18		13	2.5	2.2:1			PE8035	$389.99				91
7 - 12		16	1.6	1.6:1			PE8036	$710.00				92
8 - 16	9	12	2	1.5:1		200	PE8037	$885.00				93

DETECTORS

Biased Detectors




Frequency Range (GHz.)	Polarity	Voltage Sensitivity (mV/mW)	Flatness (dB)	Input Power (dBm)	TSS (dBm)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
500 MHz - 1	Negative	1,800	0.25	23	-54	PE8001	$805.00		See Web for Volume Pricing		94
	Positive		0.5			PE8001-P	$795.00				95
1 - 2	Negative	2,000	0.25		-52	PE8002	$610.00				96
	Positive					PE8002-P	$1,000.00				97
2 - 4	Negative		0.5			PE8003	$960.00				98
	Positive					PE8003-P	$885.00				99
4 - 8	Negative					PE8044	$690.00				1
	Positive					PE8004-P	$680.00				2
6 - 18	Negative	1,600	0.8			PE8005	$855.00				3
	Positive					PE8005-P	$750.00				4
8 - 12	Negative	1,800	0.5			PE8006	$930.00				5
	Positive					PE8006-P	$885.00				6
8 - 16	Negative		0.6			PE8007	$650.00				7
	Positive					PE8007-P	$845.00				8
8 - 18	Negative	1,600	0.7			PE8008	$785.00				9
	Positive					PE8008-P	$785.00				10
18 - 26	Negative	1,500	1			PE8009	$740.00				11
	Positive					PE8009-P	$950.00				12

Finline Detectors



Frequency Range (GHz.)	Impedance (Ohm)	Detected Output Voltage (Volts)	Frequency Response Typ. (dB/Octave)	Voltage Sensitivity (mV/mW)	Model No	1	2-4	5-9	10+	ROW
100 MHz - 12.4	50	+10.5	+/- 0.2	800	PE80T1004	$1,340.00	$1,286.40	$1,232.80	$1,179.20	13
100 MHz - 18		+9.5			PE80T1005	$1,590.00	$1,526.40	$1,462.80	$1,399.20	14

Log Detectors



Frequency Range (GHz.)	Imp. (Ohm)	Slope (mV/dB)	Input Power Max. (dBm)	Output Voltage Max. (dB)	Slew Rate (V/us)	Model No	1-4	5-9	10-24	25+	ROW
10 MHz - 3	50	40	10	2	1	PE8040	$690.00	$655.50	$621.00	$593.40	15

Phase Detectors



Frequency Range (GHz.)	Input Power Max. (dBm)	VSWR Max.	DC Voltage	Model No	1	2-4	5-9	10+	ROW
3 MHz - 300 MHz	17	17	15	PE80T4000	$1,640.00	$1,574.40	$1,508.80	$1,443.20	16
5 MHz - 25 MHz				PE80T4002	$1,370.00	$1,315.20	$1,260.40	$1,205.60	17
200 MHz - 800 MHz	10	10		PE80T4001	$1,820.00	$1,747.20	$1,674.40	$1,601.60	18

Power Detectors





Frequency Range (GHz.)	Dynamic Range (dB)	True RMS Output Voltage Typ (V)	Output Slope	VSWR	Max RF Input Power (dBm)	RF Connectors	Model No	1	2-4	5-9	10+	ROW
30 MHz - 4	80	0.62 - 1.89	Positive	1.5:1	20	SMA Female	PE80P1001	$760.01	$714.41	$676.41	$646.01	19
50 MHz - 3	60	0.12 - 2.1		1.3:1	10		PE80P1002	$712.13	$669.40	$633.80	$605.31	20
50 MHz - 5	30	0.15 - 4.95		1.4:1	15		PE80P1000	$712.13	$669.40	$633.80	$605.31	21

Schottky Zero Bias Detectors



Frequency Range (GHz.)	Imp. (Ohm)	Polarity	Voltage Sensitivity (mV/mW)	VSWR Max	Video Capacitance (pF)	Signal Level & Level Min Input (dBm)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
10 MHz - 2	50	Negative	500	1.2:1	470	-30	PE8010	$770.00	See Web for Volume Pricing	22
10 MHz - 12.4				1.6:1			PE8012	$670.00		23
		Positive					PE8012P	$695.00		24
10 MHz - 18		Negative		1.7:1			PE80T1003	$1,070.00		26
10 MHz - 18.5			450				PE8013	$815.00		27
10 MHz - 26.5			100				PE8014	$890.00		28
2 - 4			500	1.45:1	20		PE8015	$775.00		29
2 - 8				1.5:1			PE8016	$785.00		30

Threshold Detectors



Frequency Range (GHz.)	Imp. (Ohm)	Signal Level & Input Level Min. (dBm)	Input Power Max. (dBm)	Propagation Delay Typ. (ns)	DC Voltage	Model No	1	2-4	5-9	10+	ROW
2 - 18	50	-20	10	15	15	PE80T1000	$5,450.00	$5,232.00	$5,014.00	$4,796.00	31
		-45		20	12	PE80T1001	$8,900.00	$8,544.00	$8,188.00	$7,832.00	32
16 - 40		-20	17		15	PE80T1002	$6,940.00	$6,662.40	$6,384.80	$6,107.20	33

Tunnel Diode Zero Bias Detectors



Frequency Range (GHz.)	Output Polarity	VSWR Max	Pulse Video Response Risetime Typ. (ns)	Voltage Sensitivity Typ. (mV/mW)	Flatness Max. (dB)	Input Power Max. (dBm)	Video Capacitance Typ. (pF)	Model No	1-9	10-24	25-49	50+	ROW
100 MHz - 2	Negative	2:1	5	800	0.75	17	470	PE80T6000	$600.00	$570.00	$540.00	$516.00	34
	Positive					17		PE80T6001	$600.00	$570.00	$540.00	$516.00	35

Tunnel Diode Zero Bias Detectors



Frequency Range (GHz.)	Output Polarity	VSWR Max	Pulse Video Response Risetime Typ. (ns)	Voltage Sensitivity Typ. (mV/mW)	Flatness Max. (dB)	Input Power Max. (dBm)	Video Capacitance Typ. (pF)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
100 MHz - 4	Negative	2.2:1	5	800	0.75	17	470	PE80T6002	$625.00	See Web for Volume Pricing	36
	Positive					17		PE80T6003	$625.00		37
500 MHz - 1	Negative	2:1		1,000	0.5	17	100	PE80T6010	$469.99		38
	Positive					17		PE80T6011	$469.99		39
500 MHz - 18	Negative	3.5:1		400	1	17		PE80T6004	$1,450.00		40
	Positive					17		PE80T6005	$1,450.00		41
1 - 2	Negative	2:1		1,000	0.5	17	50	PE80T6012	$585.00		42
	Positive					17		PE80T6013	$585.00		43
2 - 4	Negative					17	20	PE80T6014	$610.00		44
	Positive					17		PE80T6015	$600.00		45
2 - 6	Negative	2.5:1				17		PE80T6016	$625.00		46
	Positive					17		PE80T6017	$625.00		47
2 - 18	Negative	3.5:1		500	1	17		PE80T6006	$875.00		48
	Positive					17		PE80T6007	$875.00		49
4 - 8	Negative	2.5:1		900	0.7	17		PE80T6018	$660.00		50
	Positive					17		PE80T6019	$660.00		51
6 - 12	Negative	2.7:1		800	0.6	17	10	PE80T6020	$725.00		52
	Positive					17		PE80T6021	$765.00		53
6 - 18	Negative	3:1		700	0.75	17		PE80T6008	$805.00		54
	Positive					17		PE80T6009	$850.00		55
12 - 18	Negative				0.7	17		PE80T6022	$850.00		56
	Positive					17		PE80T6023	$885.00		57
18 - 26	Negative	4:1		400	1	17	5	PE80T6024	$990.00		58
	Positive					17		PE80T6025	$990.00		59

NOISE SOURCES







Frequency Range (MHz.)	Design	Noise Output (ENR dB)	Connector	Model No	1	2-4	5-9	10+	ROW
0.01 - 2,000	Calibrated	30	SMA Female	PE85N1001	$3,120.00	$2,995.20	$2,870.40	$2,745.60	60
		15		PE85N1019	$2,970.00	$2,851.20	$2,732.40	$2,613.60	61
		30		PE85N1020	$3,210.00	$3,081.60	$2,953.20	$2,824.80	62
		15		PE85N1000	$3,080.00	$2,956.80	$2,833.60	$2,710.40	63
0.1 - 500	Calibrated, Amplified			PE85N1010	$4,130.00	$3,964.80	$3,799.60	$3,634.40	64
0.2 - 500	SMT Pin Packaged	31	SMT Pin Packaged	PE85NS4000	$215.99	$207.35	$198.71	$190.07	65
0.2 - 2,000				PE85NS4001	$251.99	$241.91	$231.83	$221.75	66
				PE85NS4003	$339.99	$326.39	$312.79	$299.19	67
0.2 - 3,000		51		PE85NS4002	$255.99	$245.75	$235.51	$225.27	68
				PE85NS4004	$443.99	$426.23	$408.47	$390.71	69
1 - 2,000	Calibrated, Amplified, Bench Top		SMA Female	PE85N1017	$20,325.00	$19,512.00	$18,699.00	$17,886.00	70
10 - 2,000	Calibrated, Amplified			PE85N1011	$4,030.00	$3,868.80	$3,707.60	$3,546.40	71
	DIP Packaged		DIP Packaged	PE85NS5000	$1,310.00	$1,257.60	$1,205.20	$1,152.80	72
				PE85NS5002	$1,390.00	$1,334.40	$1,278.80	$1,223.20	73
10 - 3,000	Calibrated, Amplified		SMA Female	PE85N1012	$4,730.00	$4,540.80	$4,351.60	$4,162.40	74
	DIP Packaged		DIP Packaged	PE85NS5001	$1,720.00	$1,651.20	$1,582.40	$1,513.60	76
				PE85NS5003	$1,800.00	$1,728.00	$1,656.00	$1,584.00	77
10 - 6,000	Calibrated	15	SMA Female	PE85N1002	$3,720.00	$3,571.20	$3,422.40	$3,273.60	78
		26		PE85N1003	$4,210.00	$4,041.60	$3,873.20	$3,704.80	79
		15		PE85N1021	$3,720.00	$3,571.20	$3,422.40	$3,273.60	80
	Calibrated, Amplified			PE85N1013	$6,080.00	$5,836.80	$5,593.60	$5,350.40	81
10 - 18,000	Calibrated	14	SMA Male	PE85N1006	$5,030.00	$4,828.80	$4,627.60	$4,426.40	82
10 - 26,000		13	3.5mm Male	PE85N1007	$6,610.00	$6,345.60	$6,081.20	$5,816.80	83
100 - 40,000		10	2.92mm Male	PE85N1008	$10,775.00	$10,344.00	$9,913.00	$9,482.00	84
100 - 60,000		7	1.85mm Male	PE85N1009	$21,400.00	$20,544.00	$19,688.00	$18,832.00	85







Frequency Range (MHz.)	Design	Noise Output (ENR dB)	Connector	Model No	1	2-4	5-9	10+	ROW
1,000 - 2,000	Calibrated	30	SMA Male	PE8505	$2,030.00	$1,948.80	$1,867.60	$1,786.40	86
1,000 - 18,000		15	SMA Female	PE85N1004	$4,470.00	$4,291.20	$4,112.40	$3,933.60	88
		23		PE85N1005	$4,650.00	$4,464.00	$4,278.00	$4,092.00	89
2,000 - 4,000		15.5	SMA Male	PE8501	$2,100.00	$2,016.00	$1,932.00	$1,848.00	90
3,700 - 4,200	Calibrated, Integral Isolator		SMA Female	PE85N1014	$4,240.00	$4,070.40	$3,900.80	$3,731.20	92
4,000 - 8,000	Calibrated		SMA Male	PE8507	$2,100.00	$2,016.00	$1,932.00	$1,848.00	93
7,200 - 8,400	Calibrated, Integral Isolator		SMA Female	PE85N1015	$4,390.00	$4,214.40	$4,038.80	$3,863.20	94
8,000 - 12,000	Calibrated	15.5	SMA Male	PE8503	$2,200.00	$2,112.00	$2,024.00	$1,936.00	95
				PE8508	$2,440.00	$2,342.40	$2,244.80	$2,147.20	96
10,700 - 12,700	Calibrated, Integral Isolator		SMA Female	PE85N1016	$4,980.00	$4,780.80	$4,581.60	$4,382.40	97
12,000 - 18,000	Calibrated	15.5	SMA Male	PE8504	$2,580.00	$2,476.80	$2,373.60	$2,270.40	98
				PE8509	$2,150.00	$2,064.00	$1,978.00	$1,892.00	99
26,500 - 40,000	Calibrated		BNC Female	PEWNS2000	$12,400.00	$11,904.00	$11,408.00	$10,912.00	1
33,000 - 50,000				PEWNS2001	$15,925.00	$15,288.00	$14,651.00	$14,014.00	2
40,000 - 60,000				PEWNS2002	$19,475.00	$18,696.00	$17,917.00	$17,138.00	3
50,000 - 75,000				PEWNS2003	$23,000.00	$22,080.00	$21,160.00	$20,240.00	4

PHASE SHIFTERS AND TRIMMERS

Adjustable Phase Trimmers



Connector	Gender	Frequency Range (MHz.)	Deg. Phase Adjustment per GHz	Max. Insertion Loss (dB)	Model No	1-9	10-24	25-49	50+	ROW
SMA	Male	DC - 18,000	10	3.4	PE8203	$239.99	$227.99	$215.99	$206.39	5

8 Bit Programmable Phase Shifter





Connector	Gender	Frequency Range (MHz.)	Deg. Phase Adjustment per GHz	Max. Insertion Loss (dB)	Model No	1	2-4	5-9	10+	ROW
2.92mm	Female	32,000 - 37,000			PE82P5003	$17,675.00	$16,968.00	$16,261.00	$15,554.00	6
SMA		500 - 2,000		13	PE82P5000	$11,100.00	$10,656.00	$10,212.00	$9,768.00	7
		6,000 - 18,000		12	PE82P5002	$18,550.00	$17,808.00	$17,066.00	$16,324.00	8

Adjustable Phase Shifter



Connector	Gender	Frequency Range (MHz.)	Deg. Phase Adjustment per GHz	Max. Insertion Loss (dB)	Model No	1	2-4	5-9	10+	ROW
2.92mm	Female	18,000 - 40,000		2.5	PE82P1000	$3,530.00	$3,388.80	$3,247.60	$3,106.40	9

Adjustable Phase Shifter


Connector	Gender	Frequency Range (MHz.)	Deg. Phase Adjustment per GHz	Max. Insertion Loss (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
SMA	Female	DC - 8,200		0.6	PE8245	$1,630.00				11
		DC - 12,700		0.7	PE8246	$1,470.00				12
		DC - 18,000		1	PE8247	$1,560.00				13
					PE8255	$3,040.00				14
		18,000 - 26,500		1.5	PE8253	$1,620.00				15

Analog Phase Shifter



Connector	Gender	Frequency Range (MHz.)	Deg. Phase Adjustment per GHz	Max. Insertion Loss (dB)	Model No	1	2-4	5-9	10+	ROW
SMA	Female	5,000 - 18,000	40	12	PE82P2000	$7,490.00	$7,190.40	$6,890.80	$6,591.20	16
		6,000 - 15,000	120	10	PE82P2001	$6,920.00	$6,643.20	$6,366.40	$6,089.60	17

POWER DIVIDERS

50 Ohm






Ports	Freq. Range (MHz.)	Connector	Gender	Maximum Power	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
2 WAY	0-67,000	1.85mm	Female	0.5 Watt	PE20DV1057	$4,160.00		See Web for Volume Pricing		18
	350-6,000	SMA		30 Watt	PE20DV1053	$353.99				19
	2,000-18,000	N			PE20DV1049	$715.00				20
		SMA			PE20DV1044	$423.99				21
	4,000-8,000				PE20DV1045	$167.99				22
	10,000-65,000	1.85mm		10 Watt	PE20DV1073	$3,090.00				23
4 WAY	375-6,000	N		30 Watt	PE20DV1050	$565.00				24
	1,000-4,000				PE20DV1051	$385.99				25
	2,000-4,000	SMA			PE20DV1046	$247.99				26
	4,000-8,000				PE20DV1047	$257.99				27
	6,000-18,000				PE20DV1048	$565.00				28
8 WAY	5-500	N		10 Watt	PE20DV1052	$740.00				29

Resistive



Ports	Freq. Range (MHz.)	Connector	Gender	Maximum Power	Model No	1-9	10-24	25-49	50+	ROW
2 WAY	0-6,000	SMA	Male	2 Watt	PE2082	$395.99	$376.19	$356.39	$340.55	30
	0-12,400	2.92mm		1 Watt	PE2063	$640.00	$608.00	$576.00	$550.40	31

Resistive





Ports	Freq. Range (MHz.)	Connector	Gender	Maximum Power	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
2 WAY	0-12,400	SMA	Male	1 Watt	PE2067	$635.00	See Web for Volume Pricing	32
	0-18,000	2.92mm			PE2064	$705.00		33
		N			PE2066	$655.00		34
		SMA			PE2068	$660.00		35
			Female		PE2084	$483.99		36
	0-26,500	2.92mm	Male		PE2065	$925.00		37
			Female		PE2083	$885.00		38
	0-50,000	2.4mm		0.5 Watt	PE20DV1056	$2,380.00		39

Reactive







Ports	Freq. Range (MHz.)	Connector	Gender	Maximum Power	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
2 WAY	2-500	BNC	Female	1 Watt	PE2000	$307.99	See Web for Volume Pricing	40
		N			PE2044	$670.00		41
		SMA			PE2070	$655.00		42
	10-1,000	N			PE2047	$775.00		43
	376-2,500	7/16 DIN		300 Watt	PE20DV1041	$249.99		44
	500-1,000	N		10 Watt	PE2032	$775.00		45
		SMA		30 Watt	PE20DV019	$155.99		46
	500-2,000			20 Watt	PE20DV009	$277.99		47
	698-2,700			10 Watt	PE20DV007	$151.99		48
	800-2,400			20 Watt	PE20DV008	$141.99		49
	1,000-2,000			30 Watt	PE20DV014	$155.99		50
	1,000-4,000			20 Watt	PE20DV013	$277.99		51
	2,000-4,000			30 Watt	PE20DV016	$155.99		52
	2,000-8,000				PE20DV000	$341.99		53
	2,000-18,000			20 Watt	PE20DV005	$481.99		54
				30 Watt	PE2028	$750.00		55
	7,000-12,400		Male	10 Watt	PE2081	$505.00		56
	8,000-12,400	N	Female		PE2036	$870.00		57
	10,000-40,000	2.92mm			PE2078	$2,510.00		58
				12 Watt	PE2077	$2,220.00		59
	10,000-50,000	2.4mm		10 Watt	PE2079A	$2,760.00		60
	12,000-18,000	N			PE2037	$1,230.00		61
3 WAY	376-2,200			500 Watt	PE20DV1040	$341.99		62
	2,000-4,000	SMA		30 Watt	PE20DV017	$255.99		63
	2,000-8,000				PE20DV001	$427.99		64
4 WAY	2-500	BNC		1 Watt	PE2001	$585.00		65
	10-1,000				PE2004	$810.00		66
	500-1,000	N		10 Watt	PE2038	$1,220.00		67
		SMA		30 Watt	PE20DV020	$247.99		68
	500-2,000				PE20DV010	$295.99		69
	800-2,500			20 Watt	PE20DV012	$175.99		70
	1,000-2,000	N		10 Watt	PE2039	$1,280.00		71
		SMA		30 Watt	PE20DV015	$247.99		72
	2,000-4,000	N			PE2040	$1,230.00		73
		SMA			PE20DV018	$237.99		74
	2,000-8,000				PE20DV002	$433.99		75
	2,000-18,000				PE20DV006	$1,020.00		76
6 WAY	1-175	BNC		1 Watt	PE2006	$785.00		77
	2,000-8,000	SMA		30 Watt	PE20DV003	$585.00		78
8 WAY	500-2,000				PE20DV011	$365.99		79
	2,000-8,000				PE20DV004	$805.00		80
12 WAY	2-500	BNC		1 Watt	PE2005	$1,060.00		81

Wilkinson







Ports	Freq. Range (MHz.)	Connector	Gender	Maximum Power	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
2 WAY	10-1,000	BNC	Female	1 Watt	PE2003	$715.00	See Web for Volume Pricing	82
	500-1,000	SMA		10 Watt	PE2008	$483.99		83
	500-2,000			30 Watt	PE20S0022	$530.00		84
	617-2,700	4.1/9.5 Mini DIN			PE20DV1033A	$369.99		85
		N			PE20DV1032A	$325.99		86
	690-2,700			10 Watt	PE2092	$173.99		87
		SMA			PE2088	$147.99		88
	800-2,500	N		50 Watt	PE20S0025	$560.00		89
		SMA		10 Watt	PE2074	$359.99		90
	1,000-2,000	N		50 Watt	PE2033	$920.00		91
		SMA		10 Watt	PE2011	$445.99		92
	1,000-26,500	2.92mm		20 Watt	PE20DV1058	$1,190.00		93
	1,000-40,000				PE20DV1059	$1,910.00		94
	2,000-4,000	SMA		10 Watt	PE2014	$373.99		95
	2,000-8,000				PE2026	$520.00		96
	2,000-40,000	2.92mm		20 Watt	PE20DV1060	$1,590.00		97
	4,000-8,000	N		30 Watt	PE2035	$840.00		98
		SMA	Male	10 Watt	PE2080	$515.00		99
	6,000-40,000	2.92mm	Female	20 Watt	PE20DV1061	$1,460.00		1
	7,000-12,400	SMA		10 Watt	PE2020	$515.00		2
	10,000-43,300	2.92mm		20 Watt	PE20DV1062	$1,330.00		3
	12,000-18,000	SMA		10 Watt	PE2023	$560.00		4
	15,000-26,500			20 Watt	PE20DV1063	$795.00		5
	18,000-40,000	2.92mm			PE20DV1064	$1,400.00		6
	26,500-40,000				PE20DV1065	$1,060.00		7
3 WAY	690-2,700	N		10 Watt	PE2093	$277.99		8
		SMA			PE2090	$261.99		9
	698-2,700	N		30 Watt	PE20DV1034A	$377.99		10
	800-2,500			50 Watt	PE20S0019	$625.00		11
4 WAY	500-1,000	SMA		30 Watt	PE2009	$645.00		12
	500-2,000				PE20S0024	$630.00		13
	690-2,700	N		10 Watt	PE2094	$343.99		14
		SMA			PE2089	$289.99		15
	698-2,700	N		30 Watt	PE20DV1036A	$600.00		16
	800-2,500	SMA			PE20S0020	$530.00		17
	2,000-18,000			10 Watt	PE2029	$1,420.00		18
	2,000-26,500			20 Watt	PE20DV1067	$1,330.00		19
	4,000-8,000	N		10 Watt	PE2041	$1,100.00		20
	6,000-40,000	2.92mm		20 Watt	PE20DV1068	$1,720.00		21
	7,000-12,400	SMA		10 Watt	PE2021	$665.00		22
	18,000-40,000	2.92mm		20 Watt	PE20DV1069	$1,590.00		23
8 WAY	500-2,000	SMA		30 Watt	PE20S0023	$725.00		24
	690-2,700	N		10 Watt	PE2095	$535.00		25
		SMA			PE2091	$365.99		26
	698-2,700	4.1/9.5 Mini DIN		30 Watt	PE20DV1039A	$1,030.00		27
		N			PE20DV1038A	$875.00		28
	800-2,500	SMA			PE20S0021	$830.00		29

Standard




Ports	Freq. Range (MHz.)	Connector	Gender	Maximum Power	Model No	1-9	10-24	25-49	50+	ROW
2 WAY	1,000-2,000	SMA	Female	30 Watt	PE20DV2102	$259.99	$246.99	$233.99	$223.59	30
	1,000-4,000	N			PE20DV2106	$585.00	$555.75	$526.50	$503.10	31
	2,000-4,000	SMA			PE20DV2104	$285.99	$271.69	$257.39	$245.95	32
	6,000-18,000				PE20DV2105	$545.00	$517.75	$490.50	$468.70	33
4 WAY	1,000-2,000				PE20DV2103	$479.99	$455.99	$431.99	$412.79	34

75 Ohm

Reactive





Ports	Freq. Range (MHz.)	Connector	Gender	Maximum Power	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
2 WAY	2-500	BNC	Female	1 Watt	PE2048	$625.00	See Web for Volume Pricing	35
	10-1,000				PE2062	$307.99		36
4 WAY	2-500				PE2049	$560.00		37

RF COMBINERS

Broadband





Frequency Range (GHz)	Ports	Connector 1	Connector 2	Power Rating	Isolation (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
20 MHz - 1	2	SMA Female	SMA Female	100 W	15	PE20S0001	$1,330.00	See Web for Volume Pricing	39
	4			200 W	12	PE20S0002	$2,070.00		40
		N Female	N Female	300 W		PE20S0003	$3,060.00		41
	2			500 W	10	PE20S0004	$3,110.00		42
80 MHz - 1	4	SMA Female	SMA Female	200 W	-12	PE20S0005	$2,070.00		43
		N Female	N Female	500 W	12	PE20S0006	$3,070.00		44
500 MHz - 2.5	2	SMA Female			13	PE20S0007	$2,130.00		45
			SMA Female	200 W	12	PE20S0008	$2,430.00		46
800 MHz - 2.5	4	N Female	N Female	600 W	6	PE20S0009	$3,180.00		47
	2		SC Female	800 W	8	PE20S0010	$2,910.00		48
			N Female	600 W		PE20S0011	$2,760.00		49
800 MHz - 4.2		SMA Female		200 W	10	PE20S0012	$3,070.00		50
	4				8	PE20S0013	$2,750.00		51
1 - 6			SMA Female	100 W	6	PE20S0014	$2,300.00		52
2 - 6	2				12	PE20S0015	$975.00		53
	4				10	PE20S0016	$1,260.00		54
		N Female	N Female	400 W		PE20S0017	$3,080.00		55

ROTARY JOINTS





Connector A	Connector B	Max. Frequency (MHz.)	Input Power	VSWR	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
SMA	PCB	DC - 6,000	30 WATT	1.15:1	PE1401	$179.99	See Web for Volume Pricing	56
2.92mm	2.92mm	DC - 18,000		1.4:1	PE1400	$215.99		57
					PE1402	$197.99		58
SMA	SMA				PE1406	$323.99		59

SURGE PROTECTORS

In-Line Surge Protectors



Impedance	Connector	Gender	Frequency Range (MHz.)	Mount Type	Maximum Power	Model No	1-9	10-24	25-49	50+	ROW
50 Ohm	4.3-10	Female to Female	698 - 2,700	Bulkhead	500 Watt	PE73SP1051	$177.99	$169.09	$160.19	$153.07	60

In-Line Surge Protectors







Impedance	Connector	Gender	Frequency Range (MHz.)	Mount Type	Maximum Power	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
50 Ohm	4.3-10	Female to Female	698 - 2,700	Bulkhead	500 Watt	PE73SP1061	$211.99	See Web for Volume Pricing	61
		Female to Male				PE73SP1062	$215.99		62
		Male to Female	555 - 4,000		200 Watt	PE73SP1070	$151.99		63
			698 - 2,700	Bulkhead	500 Watt	PE73SP1060	$177.99		64
	7/16 DIN	Female to Female	100 - 512	None	750 Watt	PE73SP1037	$195.99		65
			698 - 2,700	Bulkhead	1000 Watt	PE73SP1004	$173.99		66
			800 - 2,250		500 Watt	PE73SP1063	$131.99		67
		Female to Male	698 - 2,160	Bulkhead	500 Watt	PE73SP1008	$183.99		68
			698 - 2,700			PE73SP1006	$171.99		69
						PE73SP1007	$183.99		70
					1000 Watt	PE73SP1005	$173.99		71
		Male to Female	100 - 512	None	750 Watt	PE73SP1034	$193.99		72
			555 - 4,500		200 Watt	PE73SP1071	$159.99		73
			800 - 2,250		500 Watt	PE73SP1064	$131.99		74
			800 - 2,500	None	300 Watt	PE73SP1017	$175.99		75
	N	Female to Female	DC - 2,400	Bulkhead	50 Watt	PE73SP1040	$97.99		76
			DC - 2,500		2000 Watt	PE7301-4	$219.99		77
			DC - 3,000		40 Watt	PE73SP1039	$75.99		78
					200 Watt	PE7301-3	$211.99		79
				None		PE7301-1	$195.99		80
					2000 Watt	PE7301-2	$203.99		81
			DC - 7,000	Bulkhead	90 Watt	PE73SP1038	$57.99		82
			1.5 - 700		500 Watt	PE73SP1027	$133.99		83
					3000 Watt	PE73SP1030	$99.99		84
				None	2000 Watt	PE73SP1025	$82.99		85
			10 - 1,000	Bulkhead	1500 Watt	PE73SP1024	$90.99		86
			40 - 400	None	100 Watt	PE73SP1015	$187.99		87
						PE73SP1018	$187.99		88
			100 - 512		750 Watt	PE73SP1033	$137.99		89
						PE73SP1035	$137.99		90
			125 - 1,000	Bulkhead	200 Watt	PE73SP1029	$133.99		91
					500 Watt	PE73SP1022	$99.99		92
					375 Watt	PE73SP1021	$82.99		93
			400 - 1,200		300 Watt	PE73SP1019	$163.99		94
			698 - 2,700	Bulkhead	500 Watt	PE73SP1000	$123.99		95
			800 - 2,250		500 Watt	PE73SP1065	$113.99		96
			800 - 2,500	None	300 Watt	PE73SP1010	$165.99		97
						PE73SP1013	$165.99		98
						PE73SP1014	$165.99		99
			1,800 - 6,000	Bulkhead	10 Watt	PE73SP1050	$125.99		1
			2,000 - 6,000			PE73SP1048	$71.99		2
		Female to Male	DC - 2,400		50 Watt	PE73SP1042	$97.99		3
			DC - 7,000		90 Watt	PE73SP1041	$57.99		4
			698 - 2,700		500 Watt	PE73SP1001	$123.99		5
						PE73SP1002	$135.99		6
						PE73SP1003	$141.99		7
			2,000 - 6,000		10 Watt	PE73SP1049	$71.99		8
		Male to Female	10 - 1,000		1500 Watt	PE73SP1028	$90.99		9
			100 - 512	None	750 Watt	PE73SP1036	$135.99		10
			125 - 1,000	Bulkhead	500 Watt	PE73SP1031	$99.99		11
				None	375 Watt	PE73SP1023	$82.99		12
			800 - 2,250		500 Watt	PE73SP1066	$113.99		13
			800 - 2,500	None	300 Watt	PE73SP1011	$165.99		14
	SMA	Female to Female	DC - 5,800	Bulkhead	150 Watt	PE73SP1068	$51.99		15
		Female to Male				PE73SP1067	$51.99		16
						PE73SP1069	$51.99		17
	TNC	Female to Female	DC - 6,000		200 Watt	PE73SP1073	$52.99		18
			800 - 2,500	None	300 Watt	PE73SP1016	$165.99		19
		Female to Male	DC - 6,000	Bulkhead	200 Watt	PE73SP1072	$52.99		20
	UHF	Female to Female	1.5 - 700		2000 Watt	PE73SP1032	$95.99		21
						PE73SP1026	$87.99		22

See Our Website For Current Pricing & Real-Time Stock Availability!

Surge Protectors

Surge Protector Replacement Cartridges




Cartridge For	Maximum Power	Model No	1-24	25-49	50-99	100+	ROW
PE7301	200 Watt	PE7301-200CART	$39.19	$37.23	$35.27	$33.70	23
	2,000 Watt	PE7301-2000CART	$35.19	$33.43	$31.67	$30.26	24
PE7139 & PE7140	1,500 Watt	PE7139-CART	$24.19	$23.22	$22.50	$22.01	25

INDEX GUIDE TO SWITCHES

SWITCHES.....328

ELECTROMECHANICAL RELAY SWITCHES.....324

1M Life Cycles.....328
2M Life Cycles.....330
2.5M Life Cycles.....332
5M Life Cycles.....333
10M Life Cycles.....334
Special Applications.....334

GaN HIGH POWER SWITCHES.....340

HIGH ISOLATION SWITCHES.....339

HIGH ISOLATION USB SWITCHES.....339

MANUAL SWITCHES.....335

PIN DIODE SWITCHES.....335

SPST.....335
SPDT.....336
SP3T.....337
SP4T.....337
SP5T.....338
SP6T.....338
SP8T.....338
SP12T.....339
Transfer.....339

SMT PACKAGED ELECTROMECHANICAL SWITCHES.....334

Electromechanical Relay Switches

1M Life Cycles




Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: Non-Terminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
8 GHz	SP6T	TNC Female	NO/Non-T	60	0.6	28	50	PE71S6207	$2,310.00	See Web for Volume Pricing	1
10 GHz	SPDT		F/I, TTL, D, Non-T			12		PE71S6200	$1,390.00		2
			F/Non-T			28		PE71S6199	$1,750.00		3
	SP4T	N Female	NO/I, TTL, D, Non-T			12		PE71S6184	$2,200.00		4

1M Life Cycles





Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: NTerminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
10 GHz	SP4T	N Female	NO/I, TTL, D, NT	60	0.6	28	50	PE71S6185	$2,200.00	See Web for Volume Pricing	5
						12	160	PE71S6192	$2,530.00		6
			NO/NT			28	50	PE71S6183	$1,700.00		7
							160	PE71S6191	$2,310.00		8
	SP6T		NO/I, TTL, D, NT				50	PE71S6189	$2,420.00		9
						12	160	PE71S6196	$2,970.00		10
						28		PE71S6197	$3,130.00		11
			NO/NT			12	50	PE71S6186	$2,030.00		12
						28		PE71S6187	$2,000.00		13
						12	160	PE71S6194	$2,380.00		14
						28		PE71S6195	$2,510.00		15
12.4 GHz	SPDT		F/I, TTL, D, NT			12		PE71S6160	$1,650.00		16
						28		PE71S6161	$1,790.00		17
			F/NT		0.5		200	PE71S6058	$1,070.00		18
						12		PE71S6059	$780.00		19
					0.6		50	PE71S6150	$905.00		20
							160	PE71S6158	$1,260.00		21
						28		PE71S6159	$1,260.00		22
			L/I, TTL, D, S, NT		0.5	12	50	PE71S6156	$1,740.00		23
					0.6	28		PE71S6157	$1,650.00		24
			L/S, D, NT			12	160	PE71S6164	$1,950.00		25
						28	50	PE71S6155	$1,430.00		26
						12	160	PE71S6162	$1,730.00		27
						28		PE71S6163	$1,670.00		28
	Transfer		F/I, TTL, D, NT		0.4	12	50	PE71S6168	$2,000.00		29
						28		PE71S6169	$2,110.00		30
							160	PE71S6177	$2,250.00		31
		TNC Female			0.6	12	50	PE71S6204	$1,940.00		32
						28		PE71S6205	$2,150.00		33
		N Female	F/NT		0.4	12		PE71S6166	$1,620.00		34
						28		PE71S6167	$1,710.00		35
							160	PE71S6175	$1,920.00		36
		TNC Female			0.6	12	50	PE71S6202	$1,720.00		37
						28		PE71S6203	$1,810.00		38
		N Female	L/I, TTL, S, D, NT		0.4	12		PE71S6172	$2,530.00	See Web for Volume Pricing	39
							160	PE71S6180	$2,820.00		40
						28		PE71S6181	$2,710.00		41
			L/S, D, NT			12	50	PE71S6170	$2,100.00		42
						28		PE71S6171	$2,210.00		43
						12	160	PE71S6178	$2,400.00		44
						28		PE71S6179	$2,490.00		45
22 GHz	SPDT	SMA Female	F/T		0.6	12	20	PE71S6293	$1,570.00		46
			L/S, D, TTL, I, T			28		PE71S6300	$1,870.00		47
			L/S, D, TTL, T					PE71S6298	$1,760.00		48
	SP4T		L/S, D, T					PE71S6306	$2,920.00		49
			NO/I, T					PE71S6302	$2,480.00		50
			NO/I, TTL, D, T					PE71S6304	$3,120.00		51
			NO/T			12		PE71S6301	$2,480.00		52
	SP6T		L/I, TTL, S, D, T					PE71S6315	$3,860.00		53
						28		PE71S6316	$3,860.00		54
			L/S, D, T			12		PE71S6313	$3,500.00		55
						28		PE71S6314	$3,500.00		56

1M Life Cycles





Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: NTerminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
22 GHz	SP6T	SMA Female	NO/NT	60	0.6	12	20	PE71S6130	$1,990.00	See Web for Volume Pricing	57
						28		PE71S6131	$1,860.00		58
			NO/T			12		PE71S6309	$2,920.00		59
						28		PE71S6310	$2,850.00		60
26.5 GHz	SPDT		L/S, D, NT	50	0.5	12		PE71S6098	$880.00		61
	Transfer		F/NT	60				PE71S6110	$1,200.00		62
40 GHz	SPDT	2.92mm Female		50	0.8	28	10	PE71S6103	$2,690.00		63
			L/I, TTL, S, D, NT	55				PE71S6109	$5,040.00		64
			L/S, D, NT	50	0.9	12	5	PE71S6106	$3,970.00		65
	SP4T		L/I, TTL, S, D, NT		1			PE71S6140	$8,880.00		66
			L/I, TTL, S, D, T				3	PE71S6319	$10,075.00		67
			L/S, D, RS, T			28		PE71S6320	$10,075.00		68
			L/S, D, T					PE71S6318	$9,140.00		69
			NO/I, TTL, D, NT		0.9	12		PE71S6317	$9,140.00		70
	SP6T		L/S, I, RS, T	60	1	28		PE71S6137	$5,490.00		71
						12		PE71S6321	$10,150.00		72
			L/S, TTL, I, RS, T			28		PE71S6322	$10,150.00		73
						12		PE71S6323	$11,100.00		74
			NO/NT	50		28		PE71S6324	$7,760.00		75
	Transfer		L/S, D, NT		0.9	12	5	PE71S6143	$4,500.00		76
						28		PE71S6122	$4,170.00		77
								PE71S6123	$4,010.00		78

2M Life Cycles





Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: NTerminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
3 GHz	SPDT	SMA Female	L/NT	30		12		PE71S8001	$600.00	See Web for Volume Pricing	79
	SP4T							PE71S8002	$755.00		80
10 GHz	SPDT	N Female	F	70	0.5	12	600	PE71S6426	$915.00		81
12 GHz								PE71S6435	$1,160.00		82
						28		PE71S6438	$915.00		83
			F/I, TTL, NT			12	1000	PE71S6460	$1,580.00		84
			F/NT				200	PE71S6348	$900.00		85
						28		PE71S6397	$540.00		86
						12		PE71S6398	$540.00		87
	SP4T		NO				600	PE71S6434	$2,650.00		88
			NO/I, Solder Pins, TTL, NT	60		28	1000	PE71S6466	$3,800.00		89
			NO/Solder Pins, NT			12		PE71S6464	$3,270.00		90
	SP6T		NO/I, Solder Pins, TTL, NT					PE71S6465	$4,020.00		91
	Transfer		F/NT		0.7	28	200	PE71S6385	$1,330.00		92
								PE71S6403	$935.00		93
			F/TTL, NT					PE71S6386	$1,470.00		94

2M Life Cycles





Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: NTerminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
12 GHz	DPDT	N Female	F/I, TTL, NT	60	0.7	12	1000	PE71S6463	$2,420.00	See Web for Volume Pricing	95
			F/NT					PE71S6462	$2,080.00		96
12.4 GHz	SP6T		L/I, RS, NT		0.5		200	PE71S6072	$4,520.00		97
						28		PE71S6073	$4,150.00		98
	SP12T		L/S, AR, I, D, T		0.6		120	PE71S6082	$10,600.00		99
18 GHz	SPDT	SMA Female	F	65	0.35	12	90	PE71S6429	$433.99		1
								PE71S6436	$321.99		2
			F/I, NT				60	PE71S6351	$433.99		3
			F/NT					PE71S6347	$343.99		4
						28		PE71S6391	$343.99		5
						12		PE71S6392	$345.99		6
			F/T	60	0.5	28	100	PE71S6060	$1,450.00		7
				65	0.35	12	60	PE71S6354	$1,450.00		8
						28		PE71S6355	$1,530.00		9
					0.4			PE71S6404	$1,380.00		10
			F/TTL, NT		0.35	12		PE71S6350	$525.00		11
			L/TTL, T	60	0.5	28	100	PE71S6063	$1,810.00		12
	SP4T		NO/NT	80	0.4	12	60	PE71S6363	$1,450.00		13
						28		PE71S6408	$1,040.00		14
			NO/T			12		PE71S6368	$3,020.00		15
						28		PE71S6369	$3,140.00		16
	SP6T		NO/NT			12		PE71S6373	$1,610.00		17
						28		PE71S6409	$1,320.00		18
			NO/T			12		PE71S6380	$3,620.00		19
						28		PE71S6381	$3,620.00		20
			NO/TTL, NT			12		PE71S6374	$1,780.00		21
						24		PE71S6375	$1,780.00		22
	SP8T		L/I, RS, T	60	0.6	28	100	PE71S6080	$9,480.00		23
			NO/NT	75	0.5	12	60	PE71S6384	$2,870.00		24
	SP10T			55	0.7	28	100	PE71S6076	$5,190.00		25
	SP12T		L/I, RS, T	50	0.8			PE71S6083	$10,500.00		26
	Transfer		F	60	0.5		90	PE71S6433	$795.00		27
			F/NT			12	60	PE71S6388	$1,010.00		28
						24		PE71S6389	$970.00		29
						28	90	PE71S6400	$850.00		30
20 GHz	SP10T		NO/NT	70	0.7		60	PE71S6410	$3,790.00		31
26.5 GHz	SPDT		F	50	0.6		90	PE71S6419	$575.00		32
						12		PE71S6420	$535.00		33
						28		PE71S6421	$535.00		34
						24		PE71S6430	$535.00		35
			F/I, TTL, T			12		PE71S6468	$1,730.00		36
						28		PE71S6469	$1,570.00		37
			F/T			12	50	PE71S6356	$1,570.00		38
						28		PE71S6357	$1,550.00		39
								PE71S6467	$1,370.00		40
			F/TTL,				90	PE71S6422	$720.00		41
						12		PE71S6437	$660.00		42
	SP4T		NO/I, TTL, Solder Pins, T	70	0.7			PE71S6472	$3,830.00		43
			NO/Solder Pins, NT					PE71S6452	$1,780.00		44
						28		PE71S6453	$1,860.00		45

2M Life Cycles





Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: NTerminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
26.5 GHz	SP4T	SMA Female	NO/T	70	0.7	12	50	PE71S6370	$3,540.00	See Web for Volume Pricing	46
						28		PE71S6371	$3,410.00		47
			NO/TTL,			12	90	PE71S6423	$1,980.00		48
						28		PE71S6424	$1,850.00		49
	SP6T		F/TTL,	50	0.6	12		PE71S6427	$3,170.00		50
				70				PE71S6428	$2,210.00		51
			L/S, RS, D, T	50	0.7	28	40	PE71S6079	$5,650.00		52
			NO/I, Solder Pins, TTL, NT	70		12		PE71S6454	$2,760.00		53
						28		PE71S6455	$2,760.00		54
			NO/T			12	50	PE71S6382	$3,780.00		55
						28		PE71S6383	$3,780.00		56
	DPDT		F/I, TTL, NT	60	0.8	12		PE71S6446	$1,290.00		57
						28		PE71S6447	$1,290.00		58
40 GHz	SPDT	2.92mm Female			0.7	12		PE71S6444	$1,630.00		59
			F/NT					PE71S6443	$1,440.00		60
			L/I, TTL, S, T	50	0.8	28	10	PE71S6064	$3,840.00		61
	SP4T		NO		0.6		90	PE71S6431	$3,980.00		62
			NO/I, TTL, NT		1.3	12		PE71S6456	$5,220.00		63
				60	1.1	28		PE71S6457	$6,140.00		64
	SP6T		L/I, RS, T	50			5	PE71S6084	$6,290.00		65
			L/S, RS, D, NT					PE71S6078	$3,830.00		66
			NO/+ COM, NT	60				PE71S6459	$7,590.00		67
			NO/I, TTL, NT	50	1.3	12		PE71S6458	$5,580.00		68
	Transfer		F		0.6		90	PE71S6432	$3,100.00		69
	DPDT		F/I, TTL, NT		1			PE71S6451	$4,310.00		70
			F/NT			28		PE71S6450	$3,880.00		71
						12		PE71S6476	$3,170.00		72
50 GHz	SPDT	2.4mm Female		60	0.3	28	80	PE71S6329	$2,350.00		73
			L/NT		1.1			PE71S6330	$1,860.00		74

2.5M Life Cycles





Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: NTerminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
12.4 GHz	Transfer	N Female	F/I, NT	60	0.5	28	200	PE71S6070	$1,280.00	See Web for Volume Pricing	75
18 GHz		SMA Female	F/NT				100	PE71S6065	$1,130.00		76
						12		PE71S6066	$1,230.00		77
			L/I, NT			28		PE71S6069	$1,730.00		78
			L/I, S, NT					PE71S6067	$1,400.00		79
			L/I, TTL, S, NT					PE71S6068	$1,600.00		80
40 GHz		2.92mm Female	L/I, S, NT	50	0.8		10	PE71S6071	$2,360.00		81

5M Life Cycles





Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: NTerminated
P: Pulse
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
12 GHz	SPDT	N Female	L/I, NT	70	0.5	28	200	PE71S6399	$1,070.00	See Web for Volume Pricing	82
			L/NT			12		PE71S6349	$970.00		83
			L/TTL,			28	600	PE71S6425	$1,430.00		84
	Transfer		L/NT	60	0.7	12	200	PE71S6387	$1,310.00		85
		SMA Female			0.3		75	PE71S6390	$1,020.00		86
		N Female	L/TTL,		0.7	28	600	PE71S6439	$1,610.00		87
	DPDT		L/I, S, TTL, NT				1000	PE71S6461	$2,350.00		88
18 GHz	SPDT	SMA Female	L/I, NT	65	0.35	12	60	PE71S6353	$421.99		89
						28		PE71S6395	$565.00		90
						12		PE71S6396	$645.00		91
			L/I, T			24		PE71S6406	$1,360.00		92
			L/I, TTL, T			28		PE71S6407	$1,580.00		93
			L/NT			12		PE71S6352	$387.99		94
			L/S, I, NT			28		PE71S6393	$740.00		95
						12		PE71S6394	$540.00		96
			L/T					PE71S6358	$1,560.00		97
						28		PE71S6359	$1,480.00		98
	SP4T			80	0.4	12		PE71S6364	$2,760.00		99
						28		PE71S6365	$2,760.00		1
			NO/NT	60	0.5		100	PE71S6074	$2,340.00		2
	SP6T		L/I, S, AR, D, NT					PE71S6077	$3,680.00		3
			L/NT	80	0.4		60	PE71S6372	$3,080.00		4
			L/T			12		PE71S6376	$3,810.00		5
					0.5	28		PE71S6377	$3,620.00		6
			NO/NT	60			100	PE71S6075	$2,590.00		7
	Transfer		L/I, NT				60	PE71S6402	$920.00		8
			L/S, I, NT					PE71S6401	$1,140.00		9
	DP3T		L/I, NT	65	0.35			PE71S6405	$1,800.00		10
	SP3T		L/NT	80	0.4			PE71S6362	$2,390.00		11
26.5 GHz	SPDT		L/S, D, NT	50	0.6			PE71S6440	$775.00		12
			L/S, I, TTL, NT			12		PE71S6441	$960.00		13
						28		PE71S6442	$1,010.00		14
			L/S, I, TTL, T	40	0.5	12		PE71S6471	$2,180.00		15
			L/S, TTL, T					PE71S6470	$2,160.00		16
			L/T	50	0.6		50	PE71S6360	$1,580.00		17
						28		PE71S6361	$1,580.00		18
	SP4T		L/S, I, TTL, Solder Pins, T	70	0.7	12		PE71S6473	$4,590.00		19
						28		PE71S6474	$4,590.00		20
			L/T			12	50	PE71S6366	$3,290.00		21
						28		PE71S6367	$3,540.00		22
	SP6T					12		PE71S6378	$3,780.00		23
								PE71S6379	$3,780.00		24
			NO/I, TTL, Solder Pins, T			28		PE71S6475	$4,190.00		25
	DPDT		L/S, D, NT	60	0.8	12		PE71S6448	$1,550.00		26
			L/S, I, TTL, NT			28		PE71S6449	$1,790.00		27
40 GHz	SPDT	2.92mm Female			0.7	12		PE71S6445	$1,830.00		28
	SP4T		L/I, S, RS, T 0.05	80	0.5	24	5	PE71S6334	$8,630.00		29
			L/I, S, TTL, RS, T 0.05					PE71S6342	$9,150.00		30

5M Life Cycles



Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: NTerminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
40 GHz	SP6T	2.92mm Female	L/I, S, RS, T 0.05	80	0.9	24	5	PE71S6332	$9,210.00				31
			L/I, S, TTL, RS, T 0.05					PE71S6340	$9,650.00				32

10M Life Cycles







Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: NTerminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
6 GHz	SP6T	SMA Female	NO/NT	70	0.3	28	70	PE71S6085	$2,200.00	See Web for Volume Pricing			33
18 GHz	SPDT		F/NT	60	0.35		100	PE71S6052	$435.99				34
					0.5	12		PE71S6053	$431.99				35
			L/I, S, NT			28		PE71S6054	$675.00				36
						12		PE71S6055	$595.00				37
20 GHz			L/I, S, NT 0.03	65		24	1	PE71S6335	$1,840.00				38
			L/I, S, T 0.03					PE71S6337	$2,670.00				39
			L/I, S, TTL, NT 0.03					PE71S6336	$2,280.00				40
			L/I, S, TTL, T 0.03					PE71S6338	$2,970.00				41
	SP4T		L/I, S, RS, T 0.03	80	0.6		70	PE71S6333	$6,150.00				42
			L/I, S, TTL, RS, T 0.03					PE71S6341	$6,520.00				43
	SP6T		L/I, S, RS, T 0.03					PE71S6331	$6,830.00				44
			L/I, S, TTL, RS, T 0.03					PE71S6339	$7,240.00				45
26.5 GHz			L/GR, NT	55		28	40	PE71S6087	$2,980.00				46
			NO/TTL, NT					PE71S6088	$3,090.00				47
40 GHz	SPDT	2.92mm Female	F/I, NT	50	0.8		10	PE71S6056	$1,590.00				48
			L/I, S, NT					PE71S6057	$1,180.00				49

Special Applications



Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: NTerminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
1 GHz	A/B Coaxial	BNC Female		50	0.7	12	5	PE7100	$735.00	See Web for Volume Pricing			50
		N Female						PE7102	$565.00				51
	A/B Coaxial 75 Ohm							PE7103	$499.99				52
		BNC Female					10	PE7176	$970.00				53

SMT Packaged Electromechanical Switches



Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: NTerminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1-9	10-24	25-49	50+	ROW
8 GHz	SPDT	SMT	F/H, NT	30	0.8	24	35	PE71S6092	$387.99	$368.59	$349.19	$333.67	54

SMT Packaged Electromechanical Switches



Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: NTerminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1	2-4	5-9	10+	ROW
8 GHz	SPDT	SMT	L/H, NT	40	0.5	12	5	PE71S6413	$383.99	$360.95	$341.75	$326.39	55
						24		PE71S6414	$383.99	$360.95	$341.75	$326.39	56
18 GHz					1	12	3	PE71S6415	$510.00	$479.40	$453.90	$433.50	57
						24		PE71S6416	$510.00	$479.40	$453.90	$433.50	58
26.5 GHz					1.6		1	PE71S6418	$640.00	$601.60	$569.60	$544.00	59
						12		PE71S6417	$640.00	$601.60	$569.60	$544.00	60

Waveguide Electromechanical Relay Switches, See Page 384

Manual Switches





Impedance	Connector	Gender	Number of Output Ports	Frequency Range (MHz.)	Maximum Power	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
50 Ohm	N	Female to		DC - 1,300	500 Watt	PE7139	$297.99		See Web for Volume Pricing		61
						PE7140	$471.99				62
	SMA			DC - 22,000	50 Watt	PE7SM1000A	$1,020.00				63

PIN Diode Switches

SPST







Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	10 MHz - 1	80	1.3	200	0.1	Solder Pin	SMA Female	PE71S6230	$2,080.00	$1,996.80	$1,913.60	$1,830.40	64
	50 MHz - 26.5	30	5	150	0.5			PE71S2008	$6,780.00	$6,508.80	$6,237.60	$5,966.40	65
	50 MHz - 40	25	7.5		1		2.92mm Female	PE71S2012	$7,200.00	$6,912.00	$6,624.00	$6,336.00	66
	50 MHz - 67		9.5		0.5		1.85mm Female	PE71S2024	$9,110.00	$8,745.60	$8,381.20	$8,016.80	67
	500 MHz - 18	55	3.5	100	0.1		SMA Female	PE71S6209	$3,400.00	$3,264.00	$3,128.00	$2,992.00	68
	500 MHz - 40		5.5				2.92mm Female	PE71S6214	$4,930.00	$4,732.80	$4,535.60	$4,338.40	69
	1 - 2	80	0.9	50			SMA Female	PE71S6231	$3,130.00	$3,004.80	$2,879.60	$2,754.40	70
	1 - 18	65	3					PE71S6236	$5,120.00	$4,915.20	$4,710.40	$4,505.60	71
	2 - 4	75	1.1					PE71S6232	$2,400.00	$2,304.00	$2,208.00	$2,112.00	72
	2 - 26.5	25	4.5	150	1			PE71S2016	$6,590.00	$6,326.40	$6,062.80	$5,799.20	73
	2 - 40	30	5				2.92mm Female	PE71S2020	$6,670.00	$6,403.20	$6,136.40	$5,869.60	74
	4 - 8	75	1.8	50	0.1		SMA Female	PE71S6233	$3,210.00	$3,081.60	$2,953.20	$2,824.80	75
	8 - 12	70						PE71S6234	$2,890.00	$2,774.40	$2,658.80	$2,543.20	76
	12 - 18	65	2.8					PE71S6235	$2,970.00	$2,851.20	$2,732.40	$2,613.60	77
Reflective	10 MHz - 1	80	1	200	0.1	Solder Pin	SMA Female	PE71S6258	$1,990.00	$1,910.40	$1,830.80	$1,751.20	78
	50 MHz - 26.5	20	5	150	1			PE71S2007	$5,850.00	$5,616.00	$5,382.00	$5,148.00	79
	50 MHz - 40	25	6.5				2.92mm Female	PE71S2011	$6,270.00	$6,019.20	$5,768.40	$5,517.60	80
	50 MHz - 67	20	8.5		0.5		1.85mm Female	PE71S2023	$7,730.00	$7,420.80	$7,111.60	$6,802.40	81

SPST





Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Reflective	500 MHz - 18	55	3	100	0.1	Solder Pin	SMA Female	PE71S6220	$3,140.00	$3,014.40	$2,888.80	$2,763.20	82
	500 MHz - 40		5				2.92mm Female	PE71S6225	$3,670.00	$3,523.20	$3,376.40	$3,229.60	83
	1 - 2	80	0.75	50			SMA Female	PE71S6259	$2,130.00	$2,044.80	$1,959.60	$1,874.40	84
	1 - 18	65	2.5					PE71S6264	$3,140.00	$3,014.40	$2,888.80	$2,763.20	85
	2 - 4	75	0.85					PE71S6260	$2,310.00	$2,217.60	$2,125.20	$2,032.80	86
	2 - 26.5	20	4.5	150	1			PE71S2015	$5,510.00	$5,289.60	$5,069.20	$4,848.80	87
	2 - 40		4				2.92mm Female	PE71S2019	$5,720.00	$5,491.20	$5,262.40	$5,033.60	88
	4 - 8	75	1.5	50	0.1		SMA Female	PE71S6261	$2,590.00	$2,486.40	$2,382.80	$2,279.20	89
	8 - 12	70	1.8					PE71S6262	$2,650.00	$2,557.25	$2,464.50	$2,385.00	90
	12 - 18	65	2.5					PE71S6263	$2,740.00	$2,630.40	$2,520.80	$2,411.20	91

SPDT





Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	5 MHz - 2.15	70	2.5	100,000	0.1	D-Sub	F Female	PE71S2043	$1,630.00	$1,564.80	$1,499.60	$1,434.40	92
	5 MHz - 3	80	3.5	10,000	1		SMA Female	PE71S2036	$1,390.00	$1,334.40	$1,278.80	$1,223.20	93
	10 MHz - 1		1.3	200	0.1	Solder Pin		PE71S6237	$2,420.00	$2,323.20	$2,226.40	$2,129.60	94
	20 MHz - 4.3		3	10,000	1	D-Sub		PE71S2035	$1,390.00	$1,334.40	$1,278.80	$1,223.20	95
	20 MHz - 6	55	2.5			Solder Pin		PE71S8009	$2,050.00	$1,968.00	$1,886.00	$1,804.00	96
	70 MHz - 26.5		5	100	0.5	SMA Female		PE71S2010	$10,750.00	$10,320.00	$9,890.00	$9,460.00	97
	70 MHz - 40		7			2.92mm Female	2.92mm Female	PE71S2014	$11,075.00	$10,632.00	$10,189.00	$9,746.00	98
	100 MHz - 67	40	10.5			SMA Female	1.85mm Female	PE71S2050	$9,340.00	$8,779.60	$8,312.60	$7,939.00	99
	500 MHz - 18	55	3.75		0.1	Solder Pin	SMA Female	PE71S6210	$3,870.00	$3,715.20	$3,560.40	$3,405.60	1
	500 MHz - 40	60	6	50			2.92mm Female	PE71S6215	$6,690.00	$6,422.40	$6,154.80	$5,887.20	2
	800 MHz - 2.7	75	0.8	10,000	100		SMA Female	PE71S2041	$4,360.00	$4,185.60	$4,011.20	$3,836.80	3
	1 - 18	65	3.5	100	0.1			PE71S6241	$3,560.00	$3,417.60	$3,275.20	$3,132.80	4
	2 - 4	75	1.2		0.5	Pin		PE71S6208	$2,770.00	$2,659.20	$2,548.40	$2,437.60	5
	2 - 26.5	60	4			SMA Female		PE71S2018	$9,760.00	$9,369.60	$8,979.20	$8,588.80	6
	2 - 40	55	5.5			2.92mm Female	2.92mm Female	PE71S2022	$10,175.00	$9,768.00	$9,361.00	$8,954.00	7
	4 - 8	70	1.9		0.1	Solder Pin	SMA Female	PE71S6238	$3,480.00	$3,340.80	$3,201.60	$3,062.40	8
	8 - 12		2.2					PE71S6239	$5,170.00	$4,963.20	$4,756.40	$4,549.60	9
	12 - 18		3.5					PE71S6240	$3,310.00	$3,177.60	$3,045.20	$2,912.80	10
Reflective	10 MHz - 1	40	0.75	40,000		Solder Pin	SMA Female	PE71S8007	$3,590.00	$3,446.40	$3,302.80	$3,159.20	11
		80	1.1	200	0.1			PE71S6265	$2,210.00	$2,121.60	$2,033.20	$1,944.80	12
	20 MHz - 500 MHz	50	0.5	40,000	150			PE71S2039	$3,940.00	$3,782.40	$3,624.80	$3,467.20	13
	20 MHz - 1	40	0.75					PE71S2040	$3,940.00	$3,782.40	$3,624.80	$3,467.20	14
	20 MHz - 2.5	50	1	10,000	25			PE71S2042	$3,540.00	$3,398.40	$3,256.80	$3,115.20	15
	70 MHz - 26.5	30	3.5	100	0.5	SMA Female		PE71S2009	$8,260.00	$7,929.60	$7,599.20	$7,268.80	18
	70 MHz - 40		5.5			2.92mm Female	2.92mm Female	PE71S2013	$8,690.00	$8,342.40	$7,994.80	$7,647.20	19
	100 MHz - 500 MHz	55	0.5	40,000	250	Solder Pin	SMA Female	PE71S2038	$3,730.00	$3,580.80	$3,431.60	$3,282.40	20
							N Female	PE71S8004	$3,630.00	$3,484.80	$3,339.60	$3,194.40	21

SPDT





Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Reflective	500 MHz - 3	55	1.25	10,000	0.1	Solder Pin	SMA Female	PE71S8008	$3,880.00	$3,724.80	$3,569.60	$3,414.40	22
	500 MHz - 18		3.2	100				PE71S6221	$3,580.00	$3,436.80	$3,293.60	$3,150.40	23
	500 MHz - 40		5.5	50			2.92mm Female	PE71S6226	$4,130.00	$3,985.45	$3,840.90	$3,717.00	24
	800 MHz - 3						SMA Female	PE71S8006	$4,000.00	$3,840.00	$3,680.00	$3,520.00	25
	960 MHz - 1.3	40	0.75	10,000			N Female	PE71S8005	$3,300.00	$3,168.00	$3,036.00	$2,904.00	26
	1 - 18	65	2.5	100	0.1		SMA Female	PE71S6269	$3,420.00	$3,283.20	$3,146.40	$3,009.60	27
	2 - 4	75	0.9		1			PE71S6219	$2,550.00	$2,448.00	$2,346.00	$2,244.00	28
	2 - 26.5	30	3			SMA Female		PE71S2017	$9,260.00	$8,889.60	$8,519.20	$8,148.80	29
	2 - 40		4		0.5	2.92mm Female	2.92mm Female	PE71S2021	$9,540.00	$9,158.40	$8,776.80	$8,395.20	30
	4 - 8	70	1.6		0.1	Solder Pin	SMA Female	PE71S6266	$2,860.00	$2,745.60	$2,631.20	$2,516.80	31
	8 - 12		1.9					PE71S6267	$3,090.00	$2,966.40	$2,842.80	$2,719.20	32
	12 - 18		2.5					PE71S6268	$3,060.00	$2,937.60	$2,815.20	$2,692.80	33

SP3T





Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	10 MHz - 1	60	1.4	200	0.1	Solder Pin	SMA Female	PE71S6242	$2,610.00	$2,505.60	$2,401.20	$2,296.80	34
	500 MHz - 18	55	3.8	100				PE71S6211	$4,780.00	$4,588.80	$4,397.60	$4,206.40	35
	500 MHz - 40		6	50			2.92mm Female	PE71S6216	$6,850.00	$6,576.00	$6,302.00	$6,028.00	36
	1 - 2	60	1.25	100			SMA Female	PE71S6243	$2,850.00	$2,736.00	$2,622.00	$2,508.00	37
	1 - 18	65	3.75					PE71S6248	$3,720.00	$3,571.20	$3,422.40	$3,273.60	38
	2 - 4	75	1.5					PE71S6244	$3,030.00	$2,908.80	$2,787.60	$2,666.40	39
	4 - 8		2.5					PE71S6245	$3,450.00	$3,312.00	$3,174.00	$3,036.00	40
	8 - 12	70	2.8					PE71S6246	$4,170.00	$4,003.20	$3,836.40	$3,669.60	41
	12 - 18		3.75					PE71S6247	$3,510.00	$3,369.60	$3,229.20	$3,088.80	42
Reflective	10 MHz - 1	60	1	200	0.1	Solder Pin	SMA Female	PE71S6270	$2,660.00	$2,553.60	$2,447.20	$2,340.80	43
	500 MHz - 18	55	3.2	100				PE71S6222	$4,010.00	$3,849.60	$3,689.20	$3,528.80	44
	500 MHz - 40		5.5	50			2.92mm Female	PE71S6227	$6,370.00	$6,115.20	$5,860.40	$5,605.60	45
	1 - 2	60	1	100			SMA Female	PE71S6271	$2,760.00	$2,649.60	$2,539.20	$2,428.80	46
	1 - 18	65	2.75					PE71S6276	$3,580.00	$3,436.80	$3,293.60	$3,150.40	47
	2 - 4	75	1.2					PE71S6272	$2,950.00	$2,832.00	$2,714.00	$2,596.00	48
	4 - 8		2					PE71S6273	$3,190.00	$3,062.40	$2,934.80	$2,807.20	49
	8 - 12	70	2.4					PE71S6274	$4,350.00	$4,176.00	$4,002.00	$3,828.00	50
	12 - 18		2.75					PE71S6275	$3,370.00	$3,235.20	$3,100.40	$2,965.60	51

SP4T




Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	5 MHz - 2.15	70	2.5	100,000	0.1	D-Sub	F Female	PE71S2044	$2,230.00	$2,140.80	$2,051.60	$1,962.40	52
	5 MHz - 3		3.5	10,000	1		SMA Female	PE71S2037	$1,940.00	$1,862.40	$1,784.80	$1,707.20	53
	10 MHz - 1	60	1.5	200	0.1	Solder Pin		PE71S6249	$3,610.00	$3,465.60	$3,321.20	$3,176.80	54

SP4T





Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	500 MHz - 18	55	3.8	100	0.1	Solder Pin	SMA Female	PE71S6212	$6,190.00	$5,942.40	$5,694.80	$5,447.20	55
	500 MHz - 40	60	8	50			2.92mm Female	PE71S6217	$10,150.00	$9,744.00	$9,338.00	$8,932.00	56
	1 - 2		1.2	100			SMA Female	PE71S6250	$3,210.00	$3,081.60	$2,953.20	$2,824.80	57
	1 - 18	70	3.75					PE71S6255	$4,050.00	$3,888.00	$3,726.00	$3,564.00	58
	2 - 4	75	1.5					PE71S6251	$3,350.00	$3,216.00	$3,082.00	$2,948.00	59
	4 - 8	70	2.2					PE71S6252	$3,580.00	$3,436.80	$3,293.60	$3,150.40	60
	8 - 12		2.6					PE71S6253	$4,460.00	$4,281.60	$4,103.20	$3,924.80	61
	12 - 18		3.75					PE71S6254	$3,780.00	$3,628.80	$3,477.60	$3,326.40	62
Reflective	10 MHz - 1	60	1.2	200	0.1	Solder Pin	SMA Female	PE71S6277	$2,850.00	$2,736.00	$2,622.00	$2,508.00	63
	30 MHz - 512 MHz	50	0.75				N Female	PE71S8003	$7,060.00	$6,777.60	$6,495.20	$6,212.80	64
	500 MHz - 18	55	3.2	100	0.1		SMA Female	PE71S6223	$5,620.00	$5,395.20	$5,170.40	$4,945.60	65
	500 MHz - 40		7.5	50			2.92mm Female	PE71S6228	$8,380.00	$8,044.80	$7,709.60	$7,374.40	66
	1 - 2	60	1	100			SMA Female	PE71S6278	$3,080.00	$2,956.80	$2,833.60	$2,710.40	67
	1 - 18	70	3					PE71S6283	$3,910.00	$3,753.60	$3,597.20	$3,440.80	68
	2 - 4	75	1.1					PE71S6279	$3,270.00	$3,139.20	$3,008.40	$2,877.60	69
	2 - 6	70	2	50				PE71S6284	$3,160.00	$3,033.60	$2,907.20	$2,780.80	70
	4 - 8		1.8	100				PE71S6280	$3,500.00	$3,360.00	$3,220.00	$3,080.00	71
	6 - 12		2.5	50				PE71S6285	$3,240.00	$3,110.40	$2,980.80	$2,851.20	72
	8 - 12		2.2	100				PE71S6281	$3,610.00	$3,465.60	$3,321.20	$3,176.80	73
	12 - 18		3					PE71S6282	$3,690.00	$3,542.40	$3,394.80	$3,247.20	74

SP5T



Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	100 MHz - 20	65	3.9	75	0.5	Solder Pin	SMA Female	PE71S2045	$5,310.00	$5,097.60	$4,885.20	$4,672.80	75

SP6T



Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	100 MHz - 20	65	4.2	75	0.5	Solder Pin	SMA Female	PE71S2032	$6,130.00	$5,762.20	$5,455.70	$5,210.50	76
								PE71S2046	$5,900.00	$5,664.00	$5,428.00	$5,192.00	77

SP8T



Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	100 MHz - 20	65	6	100	0.5	Solder Pin	SMA Female	PE71S2033	$9,850.00	$9,456.00	$9,062.00	$8,668.00	78
	500 MHz - 18	55	4.5	50	0.1			PE71S6213	$9,840.00	$9,446.40	$9,052.80	$8,659.20	79

SP8T




Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	500 MHz - 40	50	10	50	0.1	Solder Pin	2.92mm Female	PE71S6218	$12,050.00	$11,568.00	$11,086.00	$10,604.00	80
Reflective	500 MHz - 18	55	4	100	0.1	Solder Pin	SMA Female	PE71S6224	$9,500.00	$9,120.00	$8,740.00	$8,360.00	81
	500 MHz - 40	45	9	50			2.92mm Female	PE71S6229	$11,775.00	$11,304.00	$10,833.00	$10,362.00	82

SP12T



Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	100 MHz - 20	65	6	100	0.5	Solder Pin	SMA Female	PE71S2034	$12,950.00	$12,432.00	$11,914.00	$11,396.00	83

Transfer



Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	10 MHz - 1	80	1.3	100	2	Solder Pin	SMA Female	PE71S6286	$3,670.00	$3,523.20	$3,376.40	$3,229.60	84
	1 - 2		1		1			PE71S6287	$4,430.00	$4,252.80	$4,075.60	$3,898.40	85
	1 - 18	65	3.1		0.5			PE71S6292	$6,660.00	$6,393.60	$6,127.20	$5,860.80	86
	2 - 4	75	1.2		1			PE71S6288	$4,120.00	$3,955.20	$3,790.40	$3,625.60	87
	4 - 8		1.9					PE71S6289	$4,090.00	$3,926.40	$3,762.80	$3,599.20	88
	8 - 12	70	2.2		0.5			PE71S6290	$4,330.00	$4,156.80	$3,983.60	$3,810.40	89
	12 - 18	65	3					PE71S6291	$4,940.00	$4,742.40	$4,544.80	$4,347.20	90

High Isolation PIN Diode Switches





Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
SPST	0 - 20	65	6	8.5	Solder Pin	SMA Female	PE71S5001	$8,000.00	$7,680.00	$7,360.00	$7,040.00	91
SPDT	0 - 18		3	12			PE71S5005	$8,310.00	$7,977.60	$7,645.20	$7,312.80	92
	0 - 20	35	4	5			PE71S5000	$5,330.00	$5,116.80	$4,903.60	$4,690.40	93
	1 - 2	90	1	75	Solder Terminals		PE71S5002	$2,350.00	$2,256.00	$2,162.00	$2,068.00	94
SP4T	0 - 20	38	3.8		Solder Pin		PE71S5006	$9,010.00	$8,649.60	$8,289.20	$7,928.80	95
	2 - 6	80	1.8	35	Solder Terminals		PE71S5003	$3,080.00	$2,956.80	$2,833.60	$2,710.40	96
	6 - 12	75	2.5	40			PE71S5004	$3,310.00	$3,177.60	$3,045.20	$2,912.80	97

High Isolation USB PIN Diode Switches




Switch Type	Frequency Band (GHz.)	Insertion Loss (dB)	Isolation (dB)	Switching Speed (µs)	Model No	1	2-4	5-9	10+	ROW
USB	0.5 - 18.0	6	60	6,000	PE71S3900	$4,280.00	$4,108.80	$3,937.60	$3,766.40	98

High Isolation USB PIN Diode Switches



Switch Type	Frequency Band (GHz.)	Insertion Loss (dB)	Isolation (dB)	Switching Speed (µs)	Model No	1	2-4	5-9	10+	ROW
USB	0.5 - 40.0	6	60		PE71S3901	$5,840.00	$5,606.40	$5,372.80	$5,139.20	99

GaN High Power Switches




Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Reflective	DC - 6	25	1.3	100	40		SMA Female	PE71S1100	$3,440.00	$3,302.40	$3,164.80	$3,027.20	1
								PE71S1105	$3,620.00	$3,475.20	$3,330.40	$3,185.60	2
	DC - 12		2	150	25			PE71S1101	$3,310.00	$3,177.60	$3,045.20	$2,912.80	3
								PE71S1106	$3,490.00	$3,350.40	$3,210.80	$3,071.20	4
	DC - 18	23	2.3	100	10			PE71S1102	$3,500.00	$3,360.00	$3,220.00	$3,080.00	5
								PE71S1107	$3,680.00	$3,532.80	$3,385.60	$3,238.40	6
	500 MHz - 6	35	1.5	250	100		N Female	PE71S1103	$4,070.00	$3,907.20	$3,744.40	$3,581.60	7
								PE71S1108	$4,250.00	$4,080.00	$3,910.00	$3,740.00	8
	DC - 6	25	2	100	40		SMA Female	PE71S1104	$5,500.00	$5,280.00	$5,060.00	$4,840.00	9
								PE71S1109	$5,680.00	$5,452.80	$5,225.60	$4,998.40	10

INDEX GUIDE TO SYNTHESIZERS AND OSCILLATORS

SYNTHESIZERS..... 341

VOLTAGE CONTROLLED OSCILLATORS.....341

0.175" Ultra Small Commercial Surface Mount Packaged VCO.....341

0.5" Commercial Surface Mount Packaged VCO.....341

0.5" Commercial Surface Mount Packaged VCO w/ Integrated Buffer Amps.....342

0.5" Commercial Surface Mount Packaged VCO w/ Low Noise.....342

0.5" Commercial Surface Mount Packaged VCO w/ Modulation Input Port.....343

0.5" Hermatically Sealed MIL Grade Surface Mount Packaged VCO.....343

Connectorized Packaged VCO w/ Field Replaceable Connectors.....343

Hi Rel Hermatic Buffer Amp.....344

Coaxial Packaged.....343

Phase Locked Orscillators.....345

Phase Locked Crystal Oscillators.....345

Reference Oscillators.....344

TCXO Oscillators.....344

SYNTHESIZERS






Type	Freq. Band (MHz.)	Typ Ref. Freq. (MHz.)	Ph. Noise @100kHz Offset (dBc/Hz)	Output Power (dBm)	2nd Harmonic	Output Connector	Model No	1	2-4	5-9	10+	ROW
USB	25 - 6,000	50	-86	-40 to 20	-25	SMA Female	PE11S3901	$7,610.00	$7,343.65	$7,077.30	$6,849.00	1
	35 - 4,400		-103	-20 to 10	-30		PE11S3900	$2,210.00	$2,121.60	$2,033.20	$1,944.80	2
Serial, TTL	1,000 - 6,400	100		15 to 20	-10		PE11S3906	$3,760.00	$3,609.60	$3,459.20	$3,308.80	3
							PE11S3907	$3,760.00	$3,609.60	$3,459.20	$3,308.80	4
							PE11S3908	$3,760.00	$3,609.60	$3,459.20	$3,308.80	5
							PE11S3909	$3,760.00	$3,609.60	$3,459.20	$3,308.80	6
							PE11S3910	$3,760.00	$3,609.60	$3,459.20	$3,308.80	7
							PE11S3911	$3,760.00	$3,609.60	$3,459.20	$3,308.80	8
							PE11S3912	$3,760.00	$3,609.60	$3,459.20	$3,308.80	9
							PE11S3913	$3,760.00	$3,609.60	$3,459.20	$3,308.80	10
	2,000 - 6,000	10	-94	14 to 17	-22		PE11S1002	$11,850.00	$11,376.00	$10,902.00	$10,428.00	11
USB	5,000 - 10,000	50	-72	-15 to 18	-25		PE11S3902	$8,990.00	$8,630.40	$8,270.80	$7,911.20	12
	10,000 - 20,000		-80	-19 to 18	-15		PE11S3903	$9,570.00	$9,235.05	$8,900.10	$8,613.00	13
	21,000 - 24,000		-88	-17 to 17	-22		PE11S3904	$7,130.00	$6,844.80	$6,559.60	$6,274.40	14
	24,000 - 27,000		-75	14 to 17			PE11S3905	$7,670.00	$7,363.20	$7,056.40	$6,749.60	15

OSCILLATORS

0.175” Ultra Small Surface Mount Packaged VCO



Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1-24	25-49	50-99	100+	ROW
125 - 250	DC - 18	8	5	-107	-10	0.5	3	PE2V000	$123.99	$117.79	$111.59	$106.63	16
200 - 400	DC - 5	6	3	-95	-14	4	7	PE2V001	$129.99	$123.49	$116.99	$111.79	17
250 - 500	DC - 20	8	5	-107	-8	1	3	PE2V002	$123.99	$117.79	$111.59	$106.63	18
500 - 1,000	DC - 19	6	10	-97	-10	4	10	PE2V003	$129.99	$123.49	$116.99	$111.79	19
800 - 1,600	DC - 18	11	5	-93	-17	4	20	PE2V004	$165.99	$157.69	$149.39	$142.75	20
1,000 - 2,000	DC - 20	10	12	-90	-7	2	20	PE2V005	$123.99	$117.79	$111.59	$106.63	21
2,000 - 2,750	DC - 10	11	11	-86	-17	6	22	PE2V006	$123.99	$117.79	$111.59	$106.63	22
2,000 - 3,000	DC - 20	9	12	-87	-14	2	24	PE2V007	$129.99	$123.49	$116.99	$111.79	23
3,120 - 3,920	DC - 11	8	10	-87	-22	10	22	PE2V008	$123.99	$117.79	$111.59	$106.63	24
3,570 - 4,580	DC - 11.5	8	12	-83	-17	4	15	PE2V009	$127.99	$121.59	$115.19	$110.07	25
4,400 - 5,000	DC - 4.5	1	5	-85	-17	5	18	PE2V010	$125.99	$119.69	$113.39	$108.35	26
4,800 - 5,200	DC - 3	1	3.3	-80	-20	4	25	PE2V011	$125.99	$119.69	$113.39	$108.35	27
4,800 - 5,700	DC - 11	8	12	-84	-20	2	20	PE2V012	$129.99	$123.49	$116.99	$111.79	28
5,180 - 5,805	DC - 10	6	11	-83	-20	5	25	PE2V013	$129.99	$123.49	$116.99	$111.79	29
5,400 - 5,900	DC - 10	8.5	11	-84	-25	5	25	PE2V014	$131.99	$125.39	$118.79	$113.51	30
6,100 - 7,000	DC - 10	5.5	5	-76	-30	5	15	PE2V015	$127.99	$121.59	$115.19	$110.07	31
7,390 - 8,060	DC - 9	4	5	-75	-22	10	40	PE2V016	$129.99	$123.49	$116.99	$111.79	32
8,300 - 9,100	DC - 10	1	5	-73	-25	5	20	PE2V017	$129.99	$123.49	$116.99	$111.79	33
9,000 - 10,000	DC - 11	7	12	-78	-30	15	50	PE2V018	$129.99	$123.49	$116.99	$111.79	34
10,000 - 11,000	DC - 11	4	12	-72	-40	15	70	PE2V019	$129.99	$123.49	$116.99	$111.79	35

0.5” Surface Mount Packaged VCO



Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1-24	25-49	50-99	100+	ROW
10 - 20	DC - 20	10	15	-120	-11	0.02	0.05	PE1V11000	$125.99	$119.69	$113.39	$108.35	36
18 - 30	DC - 12	12	12	-120	-13	0.03	0.07	PE1V11001	$125.99	$119.69	$113.39	$108.35	37
25 - 50	DC - 15	11.5	15	-120	-12	0.05	0.03	PE1V11002	$121.99	$115.89	$109.79	$104.91	38
30 - 60	DC - 15	11	15	-119	-14	0.05	0.05	PE1V11003	$119.99	$113.99	$107.99	$103.19	39

*** Phase Noise measured at 10 KHz offset frequency**

0.5” Surface Mount Packaged VCO



Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1-24	25-49	50-99	100+	ROW
40 - 80	DC - 20	12	15	-117	-14	0.05	0.05	PE1V11004	$125.99	$119.69	$113.39	$108.35	40
40 - 100	DC - 20	11.5	15	-118	-14	0.2	0.1	PE1V11005	$119.99	$113.99	$107.99	$103.19	41
50 - 100	DC - 20	12	15	-115	-12	0.05	0.1	PE1V11006	$121.99	$115.89	$109.79	$104.91	42
60 - 120	DC - 18.5	11	15	-114	-20	0.2	0.1	PE1V11007	$119.99	$113.99	$107.99	$103.19	43
75 - 150	DC - 18	11	15	-110	-20	0.2	0.4	PE1V11008	$121.99	$115.89	$109.79	$104.91	44
100 - 200	DC - 18	11	15	-113	-12	0.2	0.1	PE1V11009	$119.99	$113.99	$107.99	$103.19	45
150 - 300	DC - 20	11	15	-108	-14	1	2	PE1V11010	$125.99	$119.69	$113.39	$108.35	46
200 - 400	DC - 20	11	15	-106	-14	0.4	0.2	PE1V11011	$215.99	$205.19	$194.39	$185.75	47
300 - 400	DC - 9	11	15	-102	-18	0.6	0.5	PE1V11012	$125.99	$119.69	$113.39	$108.35	48
400 - 600	DC - 15	11	15	-102	-15	1	1.5	PE1V11013	$119.99	$113.99	$107.99	$103.19	49
400 - 800	DC - 9	8	5	-96	-14	3	1.3	PE1V11014	$119.99	$113.99	$107.99	$103.19	50
500 - 900	DC - 11.5	12	12	-95	-14	1.5	1.5	PE1V11015	$119.99	$113.99	$107.99	$103.19	51
600 - 1,000	DC - 20	12.5	15	-96	-15	0.8	0.7	PE1V11016	$123.99	$117.79	$111.59	$106.63	52
800 - 1,200	DC - 20	11.5	15	-95	-12	0.8	2.5	PE1V11017	$125.99	$119.69	$113.39	$108.35	53
1,200 - 1,800	DC - 20	11	15	-89	-12	0.5	3	PE1V11018	$125.99	$119.69	$113.39	$108.35	54
1,350 - 1,650	DC - 18	10	15		-12	1.5		PE1V11019	$119.99	$113.99	$107.99	$103.19	55
1,500 - 2,100	DC - 18	10	15		-12			PE1V11020	$119.99	$113.99	$107.99	$103.19	56
1,500 - 2,500	DC - 16	10	15		-12			PE1V11021	$125.99	$119.69	$113.39	$108.35	57
2,000 - 2,750	DC - 10	7	11		-12			PE1V11022	$125.99	$119.69	$113.39	$108.35	58
2,570 - 3,300	DC - 10	5	11		-15			PE1V11023	$125.99	$119.69	$113.39	$108.35	59
3,000 - 3,500	DC - 10	10	11	-81	-16	2.5	12	PE1V11024	$119.99	$113.99	$107.99	$103.19	60
3,120 - 3,870	DC - 10	5	11		-15			PE1V11025	$125.99	$119.69	$113.39	$108.35	61
4,000 - 5,000	DC - 15	8	15		-18			PE1V11026	$125.99	$119.69	$113.39	$108.35	62
4,260 - 5,000	DC - 10	7	11		-18			PE1V11027	$121.99	$115.89	$109.79	$104.91	63

0.5” Surface Mount Packaged VCO w/ Integrated Buffer Amps



Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1-24	25-49	50-99	100+	ROW
510 - 550	DC - 3.5	6.5	5	-106	-22	1.5	0.8	PE1V14000	$119.99	$113.99	$107.99	$103.19	64
950 - 1,100	DC - 4.5	9	5	-104	-18	0.8	0.3	PE1V14001	$119.99	$113.99	$107.99	$103.19	65
1,570 - 1,850	DC - 4.5	5	5	-101	-18	1.8	0.2	PE1V14002	$125.99	$119.69	$113.39	$108.35	66
1,600 - 3,200	DC - 20	6	5	-89	-14	4	10	PE1V14003	$123.99	$117.79	$111.59	$106.63	67
1,700 - 1,850	DC - 4.5	3.5	5	-100	-40	0.8	0.2	PE1V14004	$119.99	$113.99	$107.99	$103.19	68
1,800 - 2,000	DC - 4.5	4.5	5	-100	-20	1.5	0.6	PE1V14005	$119.99	$113.99	$107.99	$103.19	69
1,900 - 2,100	DC - 4.5	4.5	5	-102	-40	3	0.3	PE1V14006	$119.99	$113.99	$107.99	$103.19	70
2,100 - 2,300	DC - 4.5	4.5	5	-101	-35	2.5	0.3	PE1V14007	$125.99	$119.69	$113.39	$108.35	71
2,800 - 3,000	DC - 4.5	-2	5	-93	-25	2	0.8	PE1V14008	$119.99	$113.99	$107.99	$103.19	72
4,130 - 4,350	DC - 8	7.5	8	-98	-30	4	6	PE1V14009	$119.99	$113.99	$107.99	$103.19	73
4,770 - 5,010	DC - 7.5	5	8	-98	-20	4	4	PE1V14010	$119.99	$113.99	$107.99	$103.19	74

0.5” Surface Mount Packaged VCO w/ Low Noise



Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1-24	25-49	50-99	100+	ROW
305 - 425	DC - 19.5	8	5	-117	-40	1.5	4	PE1V15000	$119.99	$113.99	$107.99	$103.19	75
850 - 900	DC - 4.5	1.5	5	-113	-45	0.3	0.2	PE1V15001	$123.99	$117.79	$111.59	$106.63	76

* Phase Noise measured at 10 KHz offset frequency

0.5” Surface Mount Packaged VCO w/ Modulation Input Port



Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1-9	10-24	25-49	50+	ROW
130 - 175	DC - 15	6.5	5	-125	-25	0.1	0.2	PE1V12000	$141.99	$134.89	$127.79	$122.11	77
195 - 240	DC - 15	8.5	5	-125	-15	0.2	0.05	PE1V12001	$141.99	$134.89	$127.79	$122.11	78
243 - 270	DC - 9.5	10	8	-120	-38	0.05	0.2	PE1V12002	$147.99	$140.59	$133.19	$127.27	79
260 - 280	DC - 10	8	5	-123	-15	0.1	0.1	PE1V12003	$141.99	$134.89	$127.79	$122.11	80
380 - 400	DC - 10	4.5	5	-124	-20	0.2	0.1	PE1V12004	$141.99	$134.89	$127.79	$122.11	81
400 - 430	DC - 10	3.5	5	-123	-25	0.1	0.05	PE1V12005	$141.99	$134.89	$127.79	$122.11	82
430 - 470	DC - 10	3.5	5	-122	-25	0.2	0.05	PE1V12006	$141.99	$134.89	$127.79	$122.11	83
465 - 525	DC - 15	3.5	5	-122	-18	0.1	0.2	PE1V12007	$147.99	$140.59	$133.19	$127.27	84
650 - 700	DC - 10	7.5	8	-121	-25	0.2	0.1	PE1V12008	$141.99	$134.89	$127.79	$122.11	85

0.5” Hermetically Sealed MIL Grade Surface Mount Packaged VCO



Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1-9	10-24	25-49	50+	ROW
10 - 20	DC - 20	10	15	-120	-11	0.02	0.05	PE1V13000	$525.00	$498.75	$472.50	$451.50	86
18 - 30	DC - 12	12	12	-120	-13	0.03	0.07	PE1V13001	$525.00	$498.75	$472.50	$451.50	87
25 - 50	0.5 - 20	11.5	15	-114	-10	0.1	0.1	PE1V13002	$525.00	$498.75	$472.50	$451.50	88
30 - 60	DC - 15	11	15	-119	-14	0.05	0.05	PE1V13003	$525.00	$498.75	$472.50	$451.50	89
40 - 80	DC - 20	12	15	-117	-14	0.05	0.05	PE1V13004	$525.00	$498.75	$472.50	$451.50	90
40 - 100	DC - 20	11.5	15	-118	-14	0.2	0.1	PE1V13005	$525.00	$498.75	$472.50	$451.50	91
50 - 100	DC - 20	12	15	-115	-12	0.05	0.1	PE1V13006	$525.00	$498.75	$472.50	$451.50	92
60 - 120	DC - 18.5	11	15	-114	-20	0.2	0.1	PE1V13007	$525.00	$498.75	$472.50	$451.50	93
75 - 150	DC - 18	11	15	-110	-20	0.2	0.4	PE1V13008	$525.00	$498.75	$472.50	$451.50	94
100 - 200	DC - 18	11	15	-113	-12	0.2	0.1	PE1V13009	$525.00	$498.75	$472.50	$451.50	95
150 - 300	DC - 20	11	15	-108	-14	1	2	PE1V13010	$525.00	$498.75	$472.50	$451.50	96
200 - 400	DC - 20	11	15	-106	-14	0.4	0.2	PE1V13011	$555.00	$527.25	$499.50	$477.30	97
400 - 800	DC - 9	8	5	-96	-14	3	1.3	PE1V13012	$525.00	$498.75	$472.50	$451.50	98
1,200 - 1,800	DC - 20	11	15	-89	-12	0.5	3	PE1V13013	$525.00	$498.75	$472.50	$451.50	99
3,000 - 3,500	DC - 10	10	11	-81	-16	2.5	12	PE1V13014	$555.00	$527.25	$499.50	$477.30	1
3,700 - 4,350	DC - 7.5	4	8	-83	-25	6	15	PE1V13015	$555.00	$527.25	$499.50	$477.30	2

Connectorized Packaged VCO w/ Field Replaceable Connectors

Coaxial Packaged





Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
25 - 50	0.5 - 15	11.5	15	-120	-12	0.05	0.03	PE1V31001	$489.99		3
30 - 60	0.5 - 15	11	15	-119	-14	0.05	0.05	PE1V31002	$489.99		4
40 - 80	0.5 - 20	12	15	-117	-14	0.05	0.05	PE1V31003	$489.99		5
50 - 100	0.5 - 20	12	15	-115	-12	0.05	0.1	PE1V31005	$489.99		6
75 - 150	0.5 - 18	11	15	-110	-20	0.2	0.4	PE1V31007	$910.00		7
200 - 400	0.5 - 20	11	15	-106	-14	0.4	0.2	PE1V31009	$489.99		8
400 - 800	0.5 - 13	12	10	-94	-20	0.6	0.7	PE1V31010	$489.99		9
1,200 - 1,800	0.5 - 20	11	15	-89	-12	0.5	3	PE1V31011	$489.99		10
230 - 290	0.5 - 4.5	2	12	-107	-8.5			PE1V31015	$600.00		11
500 - 600	0.5 - 4.5	-2	12	-105	-20			PE1V31016	$600.00		12
850 - 890	DC - 5	8	12	-99	-5		5	PE1V31018	$600.00		13
900 - 960	0.5 - 4	5.5	12	-110	-15		5	PE1V31019	$600.00		14

See Web for Volume Pricing

* Phase Noise measured at 10 KHz offset frequency

Coaxial Packaged



Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
1,700 - 1,850	0.5 - 4.5	0	12	-96	-15		13	PE1V31023	$600.00		15
2,300 - 2,450	0.5 - 4.5	3	12	-101	-15		2	PE1V31025	$600.00		16
2,400 - 2,800	1 - 11	9	12	-92	-10		50	PE1V31026	$600.00		17
3,200 - 3,400	0.5 - 4.5	5	12	-88	-15		25	PE1V31027	$600.00		18
1,435 - 1,650	0.5 - 5	7	12	-90	-7		35	PE1V31021	$600.00	See Web for Volume Pricing	19
1,550 - 1,850	0.25 - 4.75	1.5	12	-99	-20		2	PE1V31022	$600.00		20
620 - 660	0.5 - 4.5	0	12	-110	-13		2	PE1V31017	$600.00		21
1,070 - 1,210	0.5 - 4.5	1.5	12	-109	-16		1	PE1V31020	$600.00		22
2,165 - 2,360	0.5 - 10	5	12	-99	-10		10	PE1V31024	$600.00		23
4,245 - 4,335	0.5 - 8	0.5	12	-87	-13		10	PE1V31028	$600.00		24
5,220 - 5,420	0.5 - 4.5	-1	12	-83	-25		10	PE1V31029	$600.00		25

Hi-REL Hermetic Buffer Amp





Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1	2-4	5-9	10+	ROW
4,000 - 8,000	DC - 18	20	12	-75	-10	0.2	1	PE1V34000	$6,100.00	$5,886.50	$5,673.00	$5,490.00	26
5,000 - 10,000	DC - 20	20	12	-64	-15	0.2	1	PE1V34001	$7,040.00	$6,758.40	$6,476.80	$6,195.20	27
38,400 - 43,200	DC - 13	13	5	-74	-30	40	0.01	PE1V34003	$12,275.00	$11,784.00	$11,293.00	$10,802.00	28

Reference Oscillators





Loop Type	Out Freq (MHz)	Ref. Type	Out Power Typ (dBm)	2nd Harmonics Typ (dBc)	Spurious Typ (dBc)	Ph Noise @100kHz Offset (dBc/Hz)	Package Type	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
Free Running	10	Internal	+7	-20	-70	-145	Surface Mount	PE19XR1000	$477.99	See Web for Volume Pricing	29
				-25		-150	Connectorized	PE19XR1003	$2,460.00		30
	50			-20			Surface Mount	PE19XR1001	$493.99		31
				-25			Connectorized	PE19XR1004	$2,510.00		32
	100			-20		-155	Surface Mount	PE19XR1002	$580.00		33
				-25		-150	Connectorized	PE19XR1005	$2,700.00		34

TCXO Oscillators

CMOS



Output Freq. (GHz)	High Level Out Voltage (V min)	Low Level Out Voltage (V max)	Temp Stability (+/- ppm)	Ph Noise @10kHz Offset (dBc/Hz)	Dimensions (in)	Model No	1-4	5-9	10-24	25+	ROW
10	4.9	0.1	2.5	-145	1.25x1.25x 0.563	PE19XL6000	$875.00	$831.25	$787.50	$752.50	35
20						PE19XL6001	$830.00	$788.50	$747.00	$713.80	36


* Phase Noise measured at 10 KHz offset frequency

Phase Locked Oscillators




Loop Type	Out Freq (MHz)	Ref. Type	Ref. Input Freq. (MHz.)	Out Power Typ (dBm)	2nd Harmonics Typ (dBc)	Spurious Typ (dBc)	Package Type	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
Phase Locked	500	External	10	7	-35	-70	Connectorized	PE19XC7000	$1,920.00	See Web for Volume Pricing	37
			100		-25			PE19XC7005	$1,820.00		38
			10				Surface Mount	PE19XP5004	$540.00		39
			100					PE19XP5009	$540.00		40
	1000		10				Connectorized	PE19XC7001	$1,920.00		41
			100					PE19XC7006	$1,850.00		42
			10				Surface Mount	PE19XP5005	$540.00		43
			100					PE19XP5010	$540.00		44
	2000		10				Connectorized	PE19XC7002	$2,200.00		45
			100					PE19XC7007	$2,200.00		46
			10				Surface Mount	PE19XP5006	$770.00		47
			100					PE19XP5011	$730.00		48
	4000		10		-35		Connectorized	PE19XC7003	$2,520.00		49
			100		-25			PE19XC7008	$2,390.00		50
			10				Surface Mount	PE19XP5007	$845.00		51
			100					PE19XP5012	$800.00		52
	6000		10				Connectorized	PE19XC7004	$2,980.00		53
			100					PE19XC7009	$2,740.00		54
			10				Surface Mount	PE19XP5008	$880.00		55
			100					PE19XP5013	$880.00		56

Phase Locked Crystal Oscillators

Loop Type	Out Freq (MHz)	Ref. Type	Ref. Input Freq. (MHz)	Out Power Typ (dBm)	2nd Harmonics Typ (dBc)	Spurious Typ (dBc)	Package Type	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
Phase-Locked Crystal	50	External	10	+7	-20	-70	Connectorized	PE19XP5002	$3,210.00		58
	100						Surface Mount	PE19XP5001	$1,020.00		59
							Connectorized	PE19XP5003	$3,320.00		60

TAPPERS

Equal Split




Frequency Range (MHz.)	Number of Ports	Maximum Power	Directivity (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
376-2,200		500		PE-T1009	$255.99	See Web for Volume Pricing	61
				PE-T1004	$216.55		62
380-2,500				PE-T1000	$239.99		63
		700		PE-T1001	$195.60		64
600-2,700		300		PE20DV1026	$249.99		65
				PE20DV1027	$317.99		66
				PE20DV1028	$283.99		67
				PE20DV1029	$359.99		68
				PE20DV1030	$307.99		69
				PE20DV1031	$373.99		70
				PE-T1012	$239.99		71

Equal Split




Frequency Range (MHz.)	Number of Ports	Maximum Power	Directivity (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
700-2,700		700		PE-T1002	$209.86	See Web for Volume Pricing	72
		500		PE-T1003	$219.99		73
				PE-T1010	$245.99		74

Unequal Split




Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
350-5,850	5	300 Watts	2	PETP1001	$307.99	See Web for Volume Pricing	75
	6		3	PETP1002	$255.99		76
				PETP1003	$307.99		77
	7		4	PE-T2006	$225.99		78
				PETP1004	$269.99		79
				PETP1005	$307.99		80
	8		5	PE-T2003	$225.99		81
				PETP1006	$255.99		82
				PETP1007	$307.99		83
	9		7	PETP1008	$255.99		84
				PETP1009	$313.99		85
	10		9	PE-T2007	$327.99		86
				PETP1010	$255.99		87
				PE-T2016	$239.99		88
				PETP1011	$246.77		89
	13		19	PE-T2018	$195.99		90
	15		30	PE-T2001	$215.99		91
				PE-T2015	$225.99		92
				PETP1012	$255.99		93
				PETP1013	$307.99		94
	20		100	PE-T2000	$213.99		95
				PETP1014	$255.99		96
				PETP1015	$307.99		97
	30		1000	PE-T2004	$213.99	See Web for Volume Pricing	98
				PETP1016	$255.99		99
				PETP1017	$307.99		1
380-6,000	6		3	PE-T2014	$195.99		2
	7		4	PE-T2011	$195.99		3
	8		5	PE-T2012	$195.99		4
	9		7	PE-T2010	$195.99		5
	11		12	PE-T2025	$195.99		6
	20		100	PE-T2017	$275.99		7
698-2,700	5			PETP1000	$204.47		8
	10		9	PE-T2016A	$287.99		9
	30		1000	PE-T2023	$303.99		10
700-2,700	5		2	PE-T2013	$247.99		11

INDEX GUIDE TO
TERMINATIONS AND MATCHING PADS

TERMINATIONS AND MATCHING PADS.....347


***MATCHING PADS*.....352**



Matching pads designed to mate with 50 ohm connectors on one end and 75 ohm connectors on the opposite end are available in a range of connector options.

Resistive Impedance Transformers.....352

***TERMINATIONS*.....347**



RF Coaxial Terminations are available in a number of connector options and frequency ranges. Power ratings for these terminations range from 1/2 watt to 500 watts of continuous power. 50 ohm and 75 ohm options are available as well.

RF Load.....347 | Feed-Thru Load.....351

TERMINATIONS

RF Load

50 Ohm







Max. Power (Watts)	Connector	Maximum Frequency.	Construction Material	VSWR Max.	Chain	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
0.25 W	Mini SMP Female	18 GHz	Gold Plated Beryllium Copper	1.35:1	No	PE6184	$65.99	See Web for Volume Pricing	1
		40 GHz		1.45:1	No	PE6182	$191.99		2
0.5 W	2.92mm Male	40 GHz	Passivated Stainless Steel	1.2:1	Yes	PE6086	$489.99		3
					No	PE6085	$351.99		4
	2.92mm Female				Yes	PE6088	$535.00		5
					No	PE6087	$535.00		6
	7/16 DIN Male	1,000 MHz	Tri-Metal Plated Brass		No	PE6146	$159.99		7
	Mini SMP Male	40 GHz	Gold Plated Beryllium Copper	1.35:1	No	PE6163	$309.99		8
	Mini SMP Female		Gold over Nickel Plated Beryllium Copper		No	PE6162	$351.99		9
	SMA Male	12.4 GHz	Passivated Stainless Steel	1.17:1	No	PE6002	$50.99		10
	SMA Female				Yes	PE6070	$115.99		11
	SMP Female	18 GHz	Gold Plated Beryllium Copper	1.35:1	No	PE6183	$47.99		12
		26.5 GHz		1.3:1	No	PE6181	$129.99		13
1 W	1.85mm Male	65 GHz	Passivated Stainless Steel	1.6:1	Yes	PE6236	$725.00		14
					No	PE6235	$640.00		15
		67 GHz			Yes	PE6TR1101	$485.99		16
					No	PE6TR1100	$447.99		17
	1.85mm Female				No	PE6TR1102	$447.99		18
	2.4mm Male	50 GHz	Passivated Stainless Steel	1.45:1	Yes	PE6179	$680.00		19
				1.2:1	Yes	PE6TR1104	$459.99		20
			Passivated Stainless Steel	1.45:1	No	PE6178	$615.00		21
				1.2:1	No	PE6TR1103	$447.99		22
	2.4mm Female				No	PE6TR1105	$447.99		23
	2.92mm Male	40 GHz	Passivated Stainless Steel	1.25:1	Yes	PE6174	$369.99		24
				1.15:1	Yes	PE6TR1107	$301.99		25
			Passivated Stainless Steel	1.25:1	No	PE6173	$333.99		26
				1.15:1	No	PE6TR1106	$289.99		27
	2.92mm Female		Passivated Stainless Steel	1.25:1	No	PE6175	$413.99		28
				1.15:1	No	PE6TR1108	$313.99		29

RF Load

50 Ohm







Max. Power (Watts)	Connector	Maximum Frequency.	Construction Material	VSWR Max.	Chain	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
1 W	3.5mm Male	34.5 GHz		1.15:1	No	PE6TR1109	$327.99		30
				1.25:1	No	PE6TR1110	$303.99		31
	3.5mm Female			1.15:1	No	PE6TR1111	$327.99		32
				1.25:1	No	PE6TR1112	$301.99		33
	BMA Plug	18 GHz		1.2:1		PE6TR1041	$209.99		34
	BMA Jack			1.3:1		PE6TR1042	$225.99		35
	Mini SMP Female			1.2:1		PE6TR1044	$69.99		36
				1.15:1	No	PE6TR1117	$65.99		37
		27 GHz		1.2:1	No	PE6TR1118	$119.99		38
		40 GHz			No	PE6TR1119	$193.99		39
		50 GHz		1.4:1	No	PE6TR1120	$301.99		40
	MMCX Male	6 GHz	Gold Plated Brass	1.35:1	No	PE6199	$35.19		41
	QMA Male	4 GHz		1.2:1		PE6TR1050	$19.59		42
					Yes	PE6TR1051	$27.79		43
	QN Male					PE6TR1038	$62.99		44
	SMA Male		Gold Plated Brass	1.1:1	No	PE6150	$8.39		45
		6 GHz	Tri-Metal Plated Brass	1.2:1	No	PE6241	$19.19		46
					No	PE6TR1014	$12.99		47
		18 GHz	Passivated Stainless Steel		Yes	PE6069	$77.99		48
				1.25:1	Yes	PE6072	$113.99		49
					No	PE6071	$72.99		50
		26.5 GHz		1.35:1	Yes	PE6078	$141.99		51
					No	PE6077	$155.99		52
	SMA Female	18 GHz		1.25:1	No	PE6073	$111.99		53
		26.5 GHz		1.35:1	Yes	PE6080	$203.99		54
					No	PE6079	$169.99		55
	SMB Plug	4 GHz	Gold Plated Brass	1.2:1	No	PE6TR1037	$31.39		56
	SMB Jack				No	PE6TR002	$14.59		57
	SMC Jack	10 GHz		1.35:1	No	PE6TR005	$11.79		58
	SMP Male	18 GHz		1.2:1		PE6TR1039	$147.99		59
			Gold over Nickel Plated Brass		No	PE6161	$265.99		60
	SMP Female			1.2:1		PE6TR1040	$109.99		61
			Gold Plated Brass		No	PE6160	$205.99		62
				1.15:1	No	PE6TR1113	$59.99		63
		27 GHz		1.2:1	No	PE6TR1114	$133.99		64
		40 GHz			No	PE6TR1115	$193.99		65
				1.3:1	No	PE6TR1116	$181.99		66
	SSMC Plug	10 GHz	Gold Plated Brass		No	PE6243	$33.59		67
2 W	2.4mm Male	50 GHz	Passivated Stainless Steel	1.45:1	No	PE6227	$399.99		68
					No	PE6242	$650.00		69
	2.4mm Female				No	PE6180	$720.00		70
	2.92mm Male	40 GHz		1.25:1	Yes	PE6177	$495.99		71
					No	PE6176	$453.99		72
	4.3-10 Male	6 GHz		1.15:1		PE6TR1045	$57.99		73
					Yes	PE6TR1046	$54.99		74
						PE6TR1047	$63.99		75
					Yes	PE6TR1048	$64.99		76
				1.25:1	No	PE6TR1121	$63.99		77
	4.3-10 Female				No	PE6TR1122	$67.99		78
	7/16 DIN Male	3 GHz	Silver Plated Brass	1.1:1		PE6190	$81.99		79
			Aluminum			PE6TR1013	$85.99		80
		6 GHz	Tri-Metal Plated Brass	1.2:1	No	PE6196	$44.79		81
	BNC Male	3 GHz		1.15:1	No	PE6TR007	$27.39		82
		4 GHz			Yes	PE6TR008	$30.19		83
			Nickel Plated Brass		No	PE6156	$33.39		84
				1.2:1	No	PE6156A	$23.19		85
	N Male		Nickel Plated Brass	1.1:1	No	PE6154	$46.99		86
		6 GHz	Tri-Metal Plated Brass	1.2:1	Yes	PE6TR010	$33.59		87
					No	PE6248	$34.99		88
					No	PE6249	$25.79		89
				1.2:1	No	PE6TR009	$23.19		90
				1.3:1	No	PE6TR012	$28.99		91

RF Load

50 Ohm







Max. Power (Watts)	Connector	Maximum Frequency.	Construction Material	VSWR Max.	Chain	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
2 W	N Male	18 GHz	Nickel Plated Brass	1.3:1	Yes	PE6075	$111.99	See Web for Volume Pricing	92
					No	PE6009	$77.99		93
	N Female	6 GHz	Tri-Metal Plated Brass	1.2:1	No	PE6TR011	$32.99		94
		18 GHz	Nickel Plated Brass		Yes	PE6076	$181.99		95
				1.3:1	No	PE6032	$101.99		96
	QMA Male	3 GHz		1.1:1		PE6TR1052	$19.99		97
		6 GHz		1.15:1	No	PE6TR1036	$44.79		98
	SMA Male	18 GHz	Passivated Stainless Steel	1.3:1	Yes	PE6082	$92.99		99
					No	PE6081	$68.99		1
		26.5 GHz	Gold Plated Stainless Steel	1.35:1	Yes	PE6TR675	$115.99		2
			Passivated Stainless Steel		Yes	PE6TR677	$111.99		3
			Gold Plated Stainless Steel		No	PE6TR671	$90.99		4
			Passivated Stainless Steel		No	PE6TR673	$103.99		5
	SMA Female	18 GHz		1.3:1	Yes	PE6084	$127.99		6
					No	PE6083	$92.99		7
	SMB Plug	4 GHz		1.2:1	No	PE6TR042	$35.39		8
	SMB Jack				No	PE6TR041	$35.39		9
	TNC Male	6 GHz	Tri-Metal Plated Brass		Yes	PE6TR014	$23.59		10
					No	PE6172	$24.39		11
				1.35:1	No	PE6TR016	$17.39		12
		18 GHz	Passivated Stainless Steel	1.25:1	Yes	PE6090	$169.99		13
					No	PE6089	$161.99		14
	TNC Female	6 GHz	Tri-Metal Plated Brass		No	PE6229	$38.39		15
				1.3:1	No	PE6TR015	$31.19		16
		18 GHz	Passivated Stainless Steel	1.25:1	Yes	PE6092	$271.99		17
					No	PE6091	$189.99		18
5 W	2.92mm Male	40 GHz	Black Anodized Aluminum Heatsink	1.45:1	No	PE6TR028	$930.00		19
	7/16 DIN Male	7 GHz	Tri-Metal Plated Brass	1.25:1	No	PE6100	$265.99		20
	7/16 DIN Female				No	PE6139	$263.99		21
	N Male	3 GHz	Aluminum	1.15:1		PE6187	$46.39		22
		6 GHz		1.25:1		PE6186	$103.99		23
		18 GHz	Black Anodized Aluminum Heatsink		No	PE6097	$179.99		24
	N Female				No	PE6098	$217.99		25
	SMA Male				No	PE6095	$151.99		26
	SMA Female				No	PE6096	$231.99		27
	TNC Male				No	PE6099	$219.99		28
	TNC Female				No	PE6138	$251.99		29
10 W	7/16 DIN Male	7 GHz	Black Anodized Aluminum Heatsink	1.25:1	No	PE6105	$411.99		30
	7/16 DIN Female				No	PE6141	$399.99		31
	BNC Male	4 GHz			No	PE6034	$221.99		32
	BNC Female				No	PE6101	$295.99		33
	N Male	6 GHz		1.15:1	No	PE6185	$141.99		34
		18 GHz		1.4:1	No	PE6035	$321.99		35
	N Female				No	PE6102	$361.99		36
	SMA Male				No	PE6036	$249.99		37
	SMA Female				No	PE6103	$335.99		38
	TNC Male				No	PE6104	$335.99		39
	TNC Female				No	PE6140	$423.99		40
20 W	4.1/9.5 Mini DIN Male	2.7 GHz	Black Anodized Aluminum	1.33:1		PE6TR1022	$555.00		41
	4.3-10 Male					PE6TR1023	$580.00		42
	N Male					PE6TR1020	$525.00		44
25 W	7/16 DIN Male	7 GHz	Black Anodized Aluminum Heatsink	1.25:1	No	PE6107	$550.00		45
		8 GHz		1.6:1		PE6209	$405.99		46
	7/16 DIN Female					PE6210	$405.99		47
	N Male	3 GHz		1.2:1	No	PE6228	$173.99		48
		18 GHz		1.6:1		PE6205	$545.00		49
				1.4:1	No	PE6106	$590.00		50

RF Load

50 Ohm







Max. Power (Watts)	Connector	Maximum Frequency.	Construction Material	VSWR Max.	Chain	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
25 W	N Female	18 GHz	Black Anodized Aluminum Heatsink	1.6:1		PE6206	$530.00		51
				1.4:1	No	PE6037	$705.00		52
	SMA Male			1.6:1		PE6203	$540.00		53
	SMA Female					PE6204	$483.99		54
				1.4:1	No	PE6038	$665.00		55
	TNC Male			1.6:1		PE6207	$580.00		56
	TNC Female					PE6208	$530.00		57
30 W	SMA Female	4.2 GHz	Chem Film Plated Aluminum	1.25:1		PE6TR1000	$261.99		58
40 W	4.1/9.5 Mini DIN Male	2.7 GHz	Black Anodized Aluminum	1.15:1		PE6TR1026	$775.00		59
	4.3-10 Male					PE6TR1027	$790.00		60
	7/16 DIN Male					PE6TR1025	$590.00		61
	N Male					PE6TR1024	$590.00		62
50 W	7/16 DIN Male	3 GHz	Black Anodized Aluminum Heatsink	1.15:1		PE6191	$447.99	See Web for Volume Pricing	64
		4 GHz		1.25:1	No	PE6169	$605.00		65
		8 GHz		1.6:1		PE6217	$625.00		66
	7/16 DIN Female					PE6218	$715.00		67
	N Male	3 GHz		1.1:1		PE6189	$299.99		68
		4 GHz		1.2:1		PE6188	$437.99		69
		8.5 GHz		1.3:1	No	PE6TR029	$379.99		70
		18 GHz		1.6:1		PE6213	$630.00		71
				1.45:1	No	PE6198	$550.00		72
	N Female	3 GHz	Aluminum	1.25:1		PE6233	$343.99		73
			Black Anodized Aluminum Heatsink	1.1:1		PE6234	$237.99		74
		18 GHz		1.6:1		PE6214	$620.00		75
				1.45:1	No	PE6039	$760.00		76
	SMA Male			1.6:1		PE6211	$640.00		77
	SMA Female	3 GHz	Nickel Plated Brass	1.25:1		PE6232	$257.99		78
		6 GHz	Chem Film Plated Aluminum			PE6TR1001	$520.00		79
		18 GHz	Black Anodized Aluminum Heatsink	1.6:1		PE6212	$605.00		80
				1.45:1	No	PE6040	$845.00		81
	TNC Male			1.6:1		PE6215	$590.00		82
	TNC Female					PE6216	$640.00		83
	4.3-10 Male	2.7 GHz	Black Anodized Aluminum	1.15:1		PE6TR1031A	$835.00		85
	7/16 DIN Male					PE6TR1029	$815.00		86
100 W	4.3-10 Male	2.7 GHz	Black Anodized Aluminum			PE6TR1035A	$1,110.00		88
	4.3-10 Female					PE6TR1035F	$1,140.00		89
	7/16 DIN Male					PE6TR1033A	$950.00		90
		3 GHz	Black Anodized Aluminum Heatsink	1.2:1	No	PE6197	$441.99		91
	7/16 DIN Female	2 GHz		1.35:1	No	PE6137	$1,110.00		93
		2.7 GHz	Black Anodized Aluminum			PE6TR1033F	$950.00		94
	BNC Female	2 GHz		1.2:1	No	PE6041	$1,090.00		97
	N Male	2.7 GHz				PE6TR1032A	$950.00		98
		4 GHz			No	PE6168	$675.00		99
	N Female	2.7 GHz				PE6TR1032F	$1,000.00		2
		8 GHz		1.5:1		PE6222	$850.00		3
	SMA Male					PE6219	$895.00		4
	SMA Female	2 GHz		1.3:1	No	PE6043	$1,150.00		5
		6 GHz	Chem Film Plated Aluminum	1.25:1		PE6TR1002	$535.00		6
		8 GHz	Black Anodized Aluminum Heatsink	1.5:1		PE6220	$800.00		7

RF Load

50 Ohm





Max. Power (Watts)	Connector	Maximum Frequency.	Construction Material	VSWR Max.	Chain	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
100 W	TNC Female	8 GHz	Black Anodized Aluminum Heatsink	1.5:1		PE6224	$610.00				9
150 W	SMA Female	3 GHz	Chem Film Plated Aluminum	1.3:1		PE6TR1003	$525.00				10
200 W	N Male	3 GHz	Black Anodized Aluminum Heatsink	1.25:1	No	PE6230	$730.00		See Web for Volume Pricing		11
	N Female					PE6231	$755.00				12
300 W	N Female	3 GHz	Chem Film Plated Aluminum	1.3:1		PE6TR1004	$635.00				13
500 W	N Female	1.2 GHz	Chem Film Plated Aluminum	1.25:1		PE6TR1005	$670.00				14
800 W	N Female	500 MHz	Chem Film Plated Aluminum	1.5:1		PE6TR1006	$830.00				15

75 Ohm




Max. Power (Watts)	Connector	Maximum Frequency.	Construction Material	VSWR Max.	Chain	Model No	1-24	25-49	50-99	100+	ROW
0.25 W	F Male	3 GHz	Nickel Plated Zinc			PE6202-100PK	$89.99	$85.49	$80.99	$77.39	16
						PE6202-25PK	$26.19	$24.88	$23.57	$22.52	17
					No	PE6202	$1.55	$1.47	$1.40	$1.33	18
1 W	BNC Male	1,000 MHz	Nickel Plated Brass		No	PE6165	$20.39	$19.37	$18.35	$17.54	19
		2 GHz	Tri-Metal Plated Brass	1.35:1	No	PE6TR004	$81.99	$77.89	$73.79	$70.51	20
2 W	BNC Male	2 GHz		1.2:1	No	PE6TR040	$23.19	$22.03	$20.87	$19.94	21
	BNC Female			1.15:1	No	PE6TR003	$77.99	$74.09	$70.19	$67.07	22

Feed-Thru Load

50 Ohm




Max. Power (Watts)	Connector Input	Connector Output	Maximum Frequency.	Construction Material	VSWR Max.	Chain	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
2 W	BNC Male	BNC Female	1,000 MHz	Tri-Metal Plated Brass	1.3:1	No	PE6TR000	$61.99				23
	N Male	N Female		Nickel Plated Brass	1.65:1	No	PE6033	$197.99		See Web for Volume Pricing		24
	SMA Male	SMA Female		Passivated Stainless Steel	1.25:1	No	PE6026	$113.99				25

75 Ohm



Max. Power (Watts)	Connector Input	Connector Output	Maximum Frequency.	Construction Material	VSWR Max.	Chain	Model No	1-24	25-49	50-99	100+	ROW
2 W	BNC Male	BNC Female	1,000 MHz	Tri-Metal Plated Brass	1.3:1	No	PE6TR001	$43.99	$41.79	$39.59	$37.83	26

Resistive Impedance Transformers







Model No	Connector A 50 Ω	Connector B 75 Ω	Max. Frequency (MHz.)	VSWR Max.	Attenuation Loss (dB)	Accuracy (dB)	1 Pc. Price	See Web for Volume Pricing			ROW
PE7006	BNC Male	BNC Female	2,000	1.2:1		±0.5	$75.99				27
PE7007	BNC Male	BNC Female	2,000	1.2:1	6		$72.99				28
PE7067	BNC Male	F Male	3,000	1.25:1	5.7	±0.5	$149.99				29
PE7066	BNC Male	F Female	3,000	1.25:1		±0.5	$169.99				30
PE7068	BNC Female	F Male	3,000	1.25:1		±0.5	$163.99				31
PE7072	N Male	F Male	3,000	1.25:1		±0.5	$175.99				32
PE70MP1002	N Male	F Female	3,000				$151.99				33
PE7071	N Male	F Female	3,000	1.25:1		±0.5	$133.99				34
PE7027	N Male	N Female	2,000	1.2:1		±0.5	$149.99	See Web for Volume Pricing			35
PE7070	N Male	N Female	3,000	1.35:1		±0.5	$165.99				36
PE7073	N Female	F Male	3,000	1.25:1		±0.5	$221.99				37
PE70MP1001	N Female	F Female	3,000				$195.99				38
PE7074	N Female	F Female	3,000	1.25:1		±0.5	$201.99				39
PE7028	N Female	N Male	500	1.35:1		±0.5	$33.99				40
PE7083	N Female	N Male	3,000	1.35:1		±0.5	$195.99				41
PE70MP1007	SMA Male	F Male	3,000				$123.99				42
PE7075	SMA Male	F Male	3,000	1.25:1		±0.5	$187.99				43
PE70MP1006	SMA Male	F Female	3,000				$135.99	See Web for Volume Pricing			44
PE7076	SMA Male	F Female	3,000	1.25:1		±0.5	$137.99				45
PE70MP1005	SMA Female	F Male	3,000				$123.99				46
PE7077	SMA Female	F Male	3,000	1.25:1		±0.5	$125.99				47
PE70MP1004	SMA Female	F Female	3,000				$147.99				48
PE7078	SMA Female	F Female	3,000	1.25:1		±0.5	$159.99				49
PE7079	TNC Male	F Female	3,000	1.25:1	5.7	±0.5	$199.99				50
PE7081	TNC Female	F Male	3,000	1.25:1	5.7	±0.5	$199.99				51
PE7082	TNC Female	F Female	3,000	1.25:1	5.7	±0.5	$137.99				52

INDEX GUIDE TO
TEST AND MESUREMENT PRODUCTS

TEST AND MEASUREMENT PRODUCTS.....353

CALIBRATION KITS AND COMPONENTS.....353

Bench Type Calibration Kits.....353
4-in-1 Calibration Kits.....354
Interchangable Connectors.....354
Coaxial RF Probes & Probe Positioning Hardware.....354

TEST CABLE ASSEMBLIES.....354

40 GHz and 67 GHz Skew Matched Cables.....354
Ruggedized Test Cable Assemblies.....355
26.5 GHz and 40 GHz Test Cables.....355
VNA Test Cable Kit.....355
50 GHz and 67 GHz Test Cable Assemblies.....356
110 GHz 1.0mm Flexible VNA Precision Cables.....356
Handheld RF Analyzer Rugged Phase Stable Cable Assemblies.....357
Phase Stable Test Cable Assemblies-50 Ohm.....357
PE-TC195 Series Phase Stable Test Cable Assemblies.....357
PE-TC151 Series Phase Stable Test Cable Assemblies.....358
Phase Stable Test Cable Assemblies-75 Ohm.....358
Semi-Rigid Pigtail Test Probes.....358

CALIBRATION KITS AND COMPONENTS

Bench Type Calibration Kits





Connector Series	Impedance (Ohms)	Frequency Range (GHz)	Cal Type	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
2.4mm	50	DC to 50	SOL	PE5CK1015	$9,880.00	See Web for Volume Pricing	1
			SOLT	PE5CK1016	$13,325.00		2
2.92mm		DC to 40	SOL	PE5CK1017	$14,275.00		3
			SOLT	PE5CK1018	$16,625.00		4
3.5mm		DC to 8.5		PE5CK1001	$4,200.00		5
		DC to 26.5	SOLT	PE5CK1000	$6,340.00		7
			SOL	PE5CK1019	$8,090.00		8
			SOLT	PE5CK1020	$8,950.00		9
7/16 DIN		DC to 7.5	SOL	PE5CK1021	$10,825.00		10
			SOLT	PE5CK1022	$15,975.00		11
7mm		DC to 18	SOL	PE5CK1023	$7,470.00		12
BNC		DC to 10		PE5CK1024	$8,990.00		13
		DC to 18	SOL	PE5CK1025	$6,190.00		15
				PE5CK1026	$8,490.00		16
F	75	DC to 3	SOLT	PE5CK1002	$3,140.00		17
				PE70MP5000	$5,440.00		18

Test & Measurement

4-in-1 Calibration Kits

Product Features

- Lightweight Portable 4-in-1 Package
- Precision 3.5mm Connectors
- Gold Plated Short Open Load Thru
- Supports 26.5 GHz SOLT Calibration
- Calibration Coefficients on Data Sheet



Connector 1	Impedance (Ohms)	Freq. Range (GHz)	Weight (lbs.)	Model No	1	2-4	5-9	10+	ROW
3.5mm Female Short Open Load Thru	50	DC to 26.5	2.752	PE5CK1012	$4,620.00	$4,435.20	$4,250.40	$4,065.60	19
3.5mm Male Short Open Load Thru				PE5CK1013	$4,680.00	$4,492.80	$4,305.60	$4,118.40	20

Interchangeable Connectors





Impedance (Ohms)	Connector Series	Frequency Range (GHz)	Gender	Polarity	Type	Model No	1	2-4	5-9	10+	ROW
50	3.5mm	DC - 26.5	Female	Standard	Connector	PE45398	$810.00	$793.80	$777.60	$761.40	21
	N	DC - 18				PE45502	$497.99	$488.03	$478.07	$468.11	22
			Male			PE45505	$560.00	$548.80	$537.60	$526.40	23

Coaxial RF Probes & Probe Positioning Hardware

Product Features

PCB RF Probe Positioner (PE5TL1000): $1,450.00

- RF PCB probe positioner holds coaxial probes
- Magnetic mounting plate
- On-Off positioner switch
- Articulated joints
- Multi-axis positioner control

Coaxial RF Microwave GS and GSG Probe Series (PE2PB1000-PE2PB1003):

- Max. Operating Frequency of 20 GHz
- RF probe Return Loss better than 10 dB
- GS and GSG Probes Feature Gold Plated Contacts
- Compliant coaxial GSG (or GS) pogo pins



RF MICROWAVE PROBES

Probe Tip Config.	Number of Ground	Pitch 1 (µm)	Pitch 2 (µm)	Connector 1	Imp. (Ω)	Freq. Max (GHz)	RL Max (dB)	IL Max (dB)	Model No	1-4	5-9	10-24	25+	ROW
GS	1	800		2.92mm Female	50	40	10	0.5	PE2PB1006	$985.00	$935.75	$886.50	$847.10	24
				3.5mm Female		20			PE2PB1002	$705.00	$669.75	$634.50	$606.30	25
	2	1500	2,500	2.92mm Female		40			PE2PB1007	$1,020.00	$969.00	$918.00	$877.20	26
				3.5mm Female		20			PE2PB1003	$725.00	$688.75	$652.50	$623.50	27
GSG		800		2.92mm Female		40			PE2PB1004	$1,060.00	$1,007.00	$954.00	$911.60	28
				3.5mm Female		20			PE2PB1000	$755.00	$717.25	$679.50	$649.30	29
	4	1500	2,500	2.92mm Female		40			PE2PB1005	$1,090.00	$1,035.50	$981.00	$937.40	30
				3.5mm Female		20			PE2PB1001	$775.00	$736.25	$697.50	$666.50	31

TEST CABLE ASSEMBLIES

40 GHz and 67 GHz Skew Matched Cables

Product Features

- 1 ps Delay match
- Excellent VSWR of 1.4:1
- 100% tested up to 67 GHz
- Extremely Flexible
- Polarity indicators on cable ends



40 GHz and 67 GHz Skew Matched Cables

Connector 1	Connector 2	Max Frequency (GHz)	Max VSWR	Typ Insertion Loss (dB/ft)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
2.92mm Male	2.92mm Male	40	1.3:1	-1	PE3CA2517-12	$640.00				32
				-1.8	PE3CA2517-24	$730.00				33
				-2.5	PE3CA2517-36	$815.00		See Web for Volume Pricing		34
				-3.3	PE3CA2517-48	$905.00				35
1.85mm Male	1.85mm Male	67	1.4:1	3.2	PE3C5835-12	$3,990.00				36
				5	PE3C5835-24	$4,250.00				37
				6.7	PE3C5835-36	$5,110.00				38
				8.2	PE3C5835-48	$5,370.00				39

Ruggedized Test Cable Assemblies

26.5 GHz and 40 GHz Test Cables

Product Features

- Rugged VNA test port extenders
- Torsion resistant connector heads
- Max phase variation +/- 2˚ with flexure to 18 GHz
- Max phase variation +/- 3˚ with flexure to 26.5 GHz
- Max phase variation +/- 5˚ with flexure to 40 GHz
- 5,000 mating cycles minimum
- 75,000 flexure cycles minimum
- Each cable is serialized and comes with RF test data
- SMA, Type-N, 2.92mm and 2.4mm configurations available



Pasternack's ruggedized VNA test cables are designed to provide customers with repeatable accurate VNA measurements. These test cables have excellent electrical properties including low insertion loss, low VSWR and phase stability of +/- 2˚ to 18 GHz with flexure. Torsion resistant connector heads are directly attached to stainless steel conduit style armoring providing a rugged design for up to 5,000 mating cycles with proper care. The cable armoring enhances amplitude and phase stability by preventing stress due to over bending while maintaining the flexibility required for testing in a lab environment. When used with the appropriate calibration kit these test cables effectively extend the test port of the VNA allowing for accurate measurements of devices that cannot be directly connected to a Network Analyzer test port.

Connector 1	Connector 2	Freq. Max (GHz)	Imp (Ohm)	VSWR	IL @fmax (dB/ft)	Length (in)	Model No	1	2-4	5-9	10+	ROW
3.5mm Male	3.5mm Male	26.5	50	1.25	0.64	Various	PE3VNA2603	Call	Call	Call	Call	40
3.5mm Female	3.5mm Female			1.3			PE3VNA2604	Call	Call	Call	Call	41
2.92mm Male	2.92mm Male			1.25			PE3VNA2605	Call	Call	Call	Call	42
2.92mm Female	2.92mm Female	40		1.38	0.83		PE3VNA4001	Call	Call	Call	Call	43
2.4mm Male	2.4mm Male						PE3VNA4002	Call	Call	Call	Call	44
2.4mm Female	2.4mm Female						PE3VNA4004	Call	Call	Call	Call	45
							PE3VNA4005	Call	Call	Call	Call	46

VNA Test Cable Kit

Vector network analyzer (VNA) test cable kit from Pasternack Enterprises. Our VNA cable kit is for Agilent, Anritsu and other vector network analyzer test equipment. This cable kit for VNA testing uses 3.5mm NMD connector ports.

VNA test cable kit includes highly flexible test cable construction that has excellent electrical characteristics with outstanding phase and amplitude stability. This Pasternack VNA cable kit incorporates a unique interchangeable head design with a 3.5mm NMD connector port. These vector network analyzer test cable connector optional components are precision models of 7mm, type N, 3.5mm and 2.92mm connectors.



Impedance (Ohms)	Connector Series	Frequency Range (GHz)	Type	Model No	1	2-4	5-9	10+	ROW
50	3.5mm NMD Female	DC - 26.5	Cable for Interchangeable Connectors	PE310-KIT	$6,410.00	$6,185.65	$5,961.30	$5,769.00	47

50 GHz and 67 GHz Test Cable Assemblies

Product Features

- Highly flexible VNA test cables up to 50 and 67 GHz
- Max phase variation +/- 6˚ to 50 GHz and +/- 8˚ to 67 GHz with flexure
- VSWR of 1.3:1 to 50 GHz and 1.4:1 to 67 GHz
- Rated up to 5,000 mating cycles
- Up to 100,000 flex cycles
- Swept right angle connector options available
- Highly flexible stainless steel braided armoring
- Designed for accurate and repeatable measurements



Connector 1	Connector 2	Freq. Max (GHz)	Imp (Ohm)	VSWR	IL @fmax (dB/ft)	Phase Stability with Flexure (Degrees)	Flex Cycles	Model No	1	2-4	5-9	10+	ROW
2.4mm Male	2.4mm Male	50	50	1.300	1.65	6.00	100,000	PE3TC0500	Call	Call	Call	Call	48
					3.7			PE3TC0500-24	$3,500.00	$3,360.00	$3,220.00	$3,080.00	
					7			PE3TC0500-48	$3,670.00	$3,523.20	$3,376.40	$3,229.60	
	2.4mm Female				1.65			PE3TC0600	Call	Call	Call	Call	49
					3.7			PE3TC0600-24	$3,530.00	$3,388.80	$3,247.60	$3,106.40	
		50		1.300	7	6.00		PE3TC0600-48	$3,710.00	$3,561.60	$3,413.20	$3,264.80	
	2.4mm Male Right Angle				1.65			PE3TC0700	Call	Call	Call	Call	50
					3.7			PE3TC0700-24	$4,090.00	$3,926.40	$3,762.80	$3,599.20	
					7			PE3TC0700-48	$4,260.00	$4,089.60	$3,919.20	$3,748.80	
1.85mm Male	1.85mm Male	67		1.400	1.95	8.00		PE3TC0800	Call	Call	Call	Call	51
					4.3			PE3TC0800-24	$3,620.00	$3,475.20	$3,330.40	$3,185.60	
					6.25			PE3TC0800-36	$3,320.00	$3,187.20	$3,054.40	$2,921.60	
					8.2			PE3TC0800-48	$3,790.00	$3,638.40	$3,486.80	$3,335.20	
	1.85mm Female				1.95			PE3TC0900	Call	Call	Call	Call	52
					4.3			PE3TC0900-24	$3,620.00	$3,475.20	$3,330.40	$3,185.60	
					6.25			PE3TC0900-36	$3,620.00	$3,475.20	$3,330.40	$3,185.60	
					8.2			PE3TC0900-48	$3,790.00	$3,638.40	$3,486.80	$3,335.20	
	1.85mm Male Right Angle				1.95			PE3TC1000	Call	Call	Call	Call	53
					4.3			PE3TC1000-24	$4,200.00	$4,032.00	$3,864.00	$3,696.00	
					8.2			PE3TC1000-48	$4,380.00	$4,204.80	$4,029.60	$3,854.40	

110 GHz 1.0mm Flexible VNA Precision Cables

Product Features

- Operating to110 GHz
- Lightweight, protective armoring
- Precision 1.0mm stainless steel connectors
- Non-conductive protective Nome® outer sleever
- Easy assembly is serialized and includes test data



Connector 1	Connector 2	Freq. Max (GHz)	Imp (Ohm)	VSWR	IL @fmax (dB/ft)	Phase Stability with Flexure (Degrees)	Length (in)	Model No	1	2-4	5-9	10+	ROW
1.0mm Male	1.0mm Male	110	50	1.5	3.12	1.5	6.0	PE3TC1220-6	$7,360.00	$7,065.60	$6,771.20	$6,476.80	54
					5.62		12.0	PE3TC1220-12	$9,850.00	$9,456.00	$9,062.00	$8,668.00	
	1.0mm Female				3.12		6.0	PE3TC1221-12	$7,690.00	$7,420.85	$7,151.70	Call	55
					5.62		12.0	PE3TC1221-12	$7,690.00	$7,420.85	$7,151.70	$6,921.00	

Handheld RF Analyzer Rugged Phase Stable Cable Assemblies

Product Features

- Designed for in-field measurements with handheld or portable analyzers
- Excellent VSWR as low as 1.2:1
- Excellent Phase Stability with Flexure as low as 1.5 degrees
- Rugged Armor provides 1200 p.s.i crush resistance plus torque resistance
- UV resistance jacket
- Each assembly is serialized and includes test data



Connector 1	Connector 2	Freq. Max (GHz)	Imp (Ohm)	VSWR	IL @fmax (dB/ft)	Phase Stability with Flexure (Degrees)	Length (in)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
N Male	7/16 DIN Male	7	50	1.2:1	2.16	1.5	60.0	PE3C4000-60	$750.00	See Web for Volume Pricing	56
					4.92		144.0	PE3C4000-144	$980.00		
	7/16 DIN Female				2.16		60.0	PE3C4001-60	$1,060.00		57
					4.92		144.0	PE3C4001-144	$1,320.00		
	N Male	9			2.52		60.0	PE3C4002-60	$615.00		58
					5.74		144.0	PE3C4002-144	$900.00		
	N Male Right Angle				2.52		60.0	PE3C4003-60	$875.00		59
					5.74		144.0	PE3C4003-144	$1,290.00		
	N Female				2.52		60.0	PE3C4004-60	$610.00		60
					5.74		144.0	PE3C4004-144	$900.00		
	N Male	18		1.3:1	2.66	2.0	39.4	PE3C4005-100CM	$745.00		61
	N Male Right Angle							PE3C4006-100CM	$990.00		62
	N Female							PE3C4007-100CM	$800.00		63
	SMA Male				3.89		60.0	PE3C4008-60	$850.00		64
	SMA Female							PE3C4009-60	$850.00		65
	TNC Male							PE3C4010-60	$1,190.00		66
	TNC Female							PE3C4011-60	$1,190.00		67
3.5mm Male	3.5mm Female	27			3.46	4.0	39.4	PE3C4012-100CM	$1,100.00		68
3.5mm Female								PE3C4013-100CM	$1,080.00		69

Phase Stable Test Cable Assemblies-50 Ohm

PE-TC195 Series Phase Stable Test Cable Assemblies

Product Features

- Phase and amplitude stability with flexure
- Small diameter, lighter weight and lower profile for high density test applications
- Phase change with flexure +/-2° to 18 GHz
- Excellent for multi-port test equipment
- Very flexible and durable cable with a min. bend radius of 1 inch
- Excellent VSWR and insertion loss
- Extra strain relief for extended connector body with booting to enhance stability and longevity
- Each serialized assembly comes with matching test data
- 5,000 mating cycles when properly mated
- In-Stock and ready to ship



Connector 1	Connector 2	Freq. Max (GHz)	Imp (Ohm)	VSWR	IL (dB/ft)	IL (dB/m)	Phase Stability with Flexure (Degrees)	Flex Cycles	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
N Male	N Female	18	50	1.25:1	0.68	2.23	2	75,000	PE3TC0104-24	$481.99	See Web for Volume Pricing	70
	N Male								PE3TC0103-24	$427.99		71
SMA Male									PE3TC0105-24	$413.99		72
	SMA Female								PE3TC0102-24	$447.99		73
		27			2.06	6.76	3		PE3TC0202-24	$695.00		74
	SMA Male	18			0.68	2.23	2		PE3TC0101-24	$393.99		75
		27			2.06	6.76	3		PE3TC0201-24	$570.00		76

See Web for other lengths

PE-TC151 Series Phase Stable Test Cable Assemblies

Product Features

- Phase and amplitude stability with flexure
- Small diameter, lighter weight and lower profile for high density test applications
- Phase change with flexure +/-5° to 18 GHz
- Excellent for multi-port test equipment
- Very flexible and durable cable with a min. bend radius of 0.75 inches
- Excellent VSWR and insertion loss
- Extra strain relief for extended connector body with booting to enhance stability and longevity
- Each serialized assembly comes with matching test data
- 5,000 mating cycles when properly mated
- In-Stock and ready to ship



Connector 1	Connector 2	Freq. Max (GHz)	Imp (Ohm)	VSWR	IL (dB/ft)	IL (dB/m)	Phase Stability with Flexure (Degrees)	Flex Cycles	Model No	1-9	10-24	25+	ROW
N Male	N Male	18	50	1.3:1	0.85	2.79	5	75,000	PE3TC0302-24	$353.99	$336.29	$318.59	77
SMA Male									PE3TC0303-24	$337.99	$321.09	$304.19	78
	SMA Male								PE3TC0301-24	$289.99	$275.49	$260.99	79
		27							PE3TC0401-24	$493.99	$469.29	$444.59	80

See Web for other lengths

Phase Stable Test Cable Assemblies-75 Ohm

Product Features

- Phase and amplitude stability with flexure
- Small diameter, lighter weight and lower profile for high density test applications
- Very flexible and durable cable with a min. bend radius of 0.75 inches
- Each serialized assembly comes with matching test data



Connector 1	Connector 2	Freq. Max (GHz)	Imp (Ohm)	VSWR	IL (dB/ft)	IL (dB/m)	Phase Stability with Flexure (Degrees)	Flex Cycles	Model No	1-9	10-24	25+	ROW
N Male	F Male	3	75	1.16:1	0.193	0.63	5	100,000	PE3CA1031-60cm	$323.99	$307.79	$291.59	81
	N Male								PE3CA1032-60cm	$367.99	$349.59	$331.19	82

See Web for other lengths

Semi-Rigid Pigtail Test Probes

Product Features

- Operating to 6 GHz
- SMA Female connectors
- Excellent VSWR of 1.3:1
- Straight-cut and pre-stripped probe ends available



Connector 1	Cable	Lead	Freq. Max (GHz)	Imp (Ohm)	VSWR	IL @fmax (dB/ft)	Length (in)	Model No	1-24	25-49	50-99	100+	ROW
SMA Female	PE-020SR	Straight Cut Lead	6	50	1.35:1	0.43	3.0	PE3CA1107-3	$74.99	$71.24	$67.49	$64.49	83
		Trimmed Lead						PE3CA1104-3	$117.99	$112.09	$106.19	$101.47	84
	PE-034SR	Straight Cut Lead				0.28		PE3CA1102-3	$40.99	$38.94	$36.89	$35.25	85
		Trimmed Lead						PE3CA1105-3	$46.99	$44.64	$42.29	$40.41	86
	PE-047SR	Straight Cut Lead				0.20		PE3CA1103-3	$38.59	$36.66	$34.73	$33.19	87
		Trimmed Lead						PE3CA1106-3	$48.99	$46.54	$44.09	$42.13	88

Semi-Rigid Pigtail Test Probes

Connector 1	Cable	Lead	Freq. Max (GHz)	Imp (Ohm)	VSWR	IL @fmax (dB/ft)	Length (in)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
SMA Female 2 Hole Flange	PE-SR047FL	Straight Cut Lead	18	50	1.4:1		3.0	PE3C0643-3	$59.99		See Web for Volume Pricing		89
SMA Female		Straight Cut Lead						PE3C1057-3	$68.99				90
SMA Female 4 Hole Flange	PE-SR405FL	Straight Cut Lead			1.5:1			PE3C1545-3	$70.99				91
SMA Female	PE-SR047FL	Trimmed Lead			1.4:1			PE3C8133-3	$84.99				92
SMA Female 2 Hole Flange		Trimmed Lead						PE3C8134-3	$65.99				93
SMA Female 4 Hole Flange		Trimmed Lead						PE3C8135-3	$127.99				94
		Straight Cut Lead						PE3C8136-3	$127.99				95
SMA Male		Trimmed Lead	20					PE3C8137-3	$74.99				96
		Straight Cut Lead						PE3C8138-3	$74.99				97
SMA Female	PE-SR405FL	Trimmed Lead	18					PE3C8139-3	$46.39				98
		Straight Cut Lead						PE3C8140-3	$46.39				99
SMA Female 2 Hole Flange		Trimmed Lead						PE3C8141-3	$65.99				1
		Straight Cut Lead						PE3C8142-3	$65.99				2
SMA Female 4 Hole Flange		Trimmed Lead			1.5:1			PE3C8143-3	$73.99				3
SMA Male		Trimmed Lead			1.4:1			PE3C8144-3	$45.79				4
SMA Female	PE-SR405FLJ	Trimmed Lead						PE3C8145-3	$42.99				5
		Straight Cut Lead						PE3C8146-3	$42.99				6
SMA Male	PE-SR405FL	Straight Cut Lead						PE39395-3	$48.59				7

See Web for other lengths

See Our Website For Current Pricing & Real-Time Stock Availability!

INDEX GUIDE TO TOOLS

TOOLS.....355

CABLE CUTTER.....355

CRIMP TOOL DIES.....357

CRIMP TOOLS.....357

INSERTION / EXTRACTION TOOL.....355

TORQUE WRENCHES.....356

Torque Wrenches





Type	Bit Hex Size (in.)	Preset Torque (in.-lbs.)	Design	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
1.0mm	5/16 inch	4	Break-Over	PE5019-16	$285.99				1
3.5mm, 2.92mm		8	Break-Over	PE5019-1A	$275.99				2
4.3-10	5/8 inch	44.3	Break-Over	PE5020	$251.99				3
	7/8 inch	44.3	Break-Over	PE5021	$251.99				4
7/16 DIN	27 mm	20	Break-Over	PE5019-21	$271.99				5
7mm, N	5/16 inch	14	Click Type	PE5011-3	$447.99				6
N	5/32 inch	14	Break-Over	PE5019-6	$283.99				7
	1/4 inch	8	Break-Over	PE5019-3	$283.99				8
		8	Break-Over	PE5019-5	$285.99				9
	25/32 inch	14	Click Type	PE5011-7	$361.99				10
N, 7mm	1/4 inch	14	Break-Over	PE5019-4	$283.99				11
N, SC	5/8 inch	8	Break-Over	PE5019-7	$283.99				12
		14	Break-Over	PE5019-8	$283.99				13
	20 mm	14	Click Type	PE5011-6	$435.99				14
NEX10	7/16 inch	26.5	Break-Over	PE5022	$251.99				15
SMA	5/16 inch	5	Break-Over	PE5019-19A	$275.99				16
SMA, 2.92mm	15/64 inch	8	Click Type	PE5011-1	$291.99				17
SMC	5/16 inch	3	Click Type	PE5011-2	$403.99				18
	13/16 inch	3	Break-Over	PE5019-11	$285.99				19
SSMA	5/16 inch	8.1	Break-Over	PE5019-14	$301.99				20
	20 mm	8	Click Type	PE5011-5	$411.99				21
	13/16 inch	5	Break-Over	PE5019-13	$285.99				22
SSMC		2	Break-Over	PE5019-12	$283.99				23
TNC	15/64 inch	6	Break-Over	PE5019-18	$305.99				24
	1/4 inch	6	Break-Over	PE5019-17	$285.99				25
	5/8 inch	12	Break-Over	PE5019-9	$283.99				26
	3/4 inch	12	Break-Over	PE5019-10	$283.99				27
		13	Click Type	PE5011-8	$385.99				28
		14	Click Type	PE5011-4	$409.99				29

Crimp Tools





Type	Hex Size (in.)	Compatible Dies	Cable Type	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
Crimp Tools	0.100, 0.429		RG9, RG11, RG87A, RG149, RG165, RG213, RG214, RG216, RG225, RG393	PE5007	$201.99				30
Crimp Tool Kit	0.042, 0.068, 0.080, 0.100, 0.128, 0.151, 0.178, 0.213, 0.255, 0.324, 0.429	- - -	RG5, RG6, RG8, RG9, RG11, RG21, RG55, RG58, RG59, RG62, RG87A, RG140, RG141, RG142, RG143, RG165, RG174, RG179, RG180, RG187, RG188, RG195, RG210, RG212, RG213, RG214, RG216, RG222, RG223, RG225, RG303, RG304, RG316, RG393, RG400	PE5004-KIT	$457.99				31
Crimp Tool, Scissor style, No Die	- - -	PE5010-1, PE5010-2, PE5010-3, PE5010-4, PE5010-5 and PE5010-6	- - -	PE5008	$458.07		See Web for Volume Pricing		32
Crimp Tool, Straight Style, No Die	- - -	PE5010-1, PE5010-2, PE5010-3, PE5010-4, PE5010-5 and PE5010-6	- - -	PE5009	@232.97l				33
Crimp Tool for Compression Connectors	- - -	- - -	RG6, RG11, RG59	PE5012	$179.99				34

Crimp Tool Dies





Type	Hex Size (in.)	Compatible Crimp Tools	Cable Type	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
Dies, Crimp Tool	0.213, 0.068	PE5008 and PE5009	RG58, RG142, RG223, RG400	PE5010-1	$298.05		See Web for Volume Pricing		35
	0.255, 0.068		RG8X, RG59, RG62, PE-C240	PE5010-3	$252.80				

INDEX GUIDE TO
WAVEGUIDE PRODUCTS

WAVEGUIDE ANTENNAS.....364

WAVEGUIDE ANTENNAS.....364 | *WG ANTENNA ACCESSORIES.....372*

Pasternack offers a large selection of waveguide antennas from WR-284 to WR-15 (2.6 GHz to 75 GHz) in a variety of flanges and gain. Both UG and CPR/CMR style flanges are available. Most of the gain horn antennas can be purchased already assembled with a waveguide to coax adapter.



WAVEGUIDE BENDS.....376



Pasternack offers a selection of E and H plane waveguide bends of various flanges and interfaces, covering the frequency range from 5.85 GHz to 18 GHz with VSWR as low as 1.08:1.

WAVEGUIDE FILTERS.....376

BANDPASS.....376

Pasternack offers a selection of high performance waveguide bandpass filters, covering the frequency range from 20.2 GHz to 40 GHz with WR-28 and WR-42 interfaces. These filters exhibit excellent out-of-band rejection making them ideally suited to receiver front-end or transmitter applications.



WAVEGUIDE BULKHEAD ADAPTERS.....377



The Pasternack series of rectangular waveguide bulkhead flange mount adapters are mounted to the panel of equipment with screws. Once mounted, waveguides flanges can be attached to the adapter on both sides of the bulkhead adapter to allow a signal path through the panel.

WAVEGUIDE CIRCULATORS.....378

Pasternack offers a wide variety of circulators and waveguide circulators to fit your needs. These unique devices enable two signals to use one channel. These waveguide circulators cover the frequency range from 7.05 GHz to 40 GHz with VSWR as low as 1.3:1.



WAVEGUIDE CONVERTERS.....378

MIXER DOWN CONVERTERS.....378 *MIXER UP CONVERTERS.....378*



Pasternack offers a series of Millimeter Wave Up and Down Converter Mixers that cover popular Ka, Q, U, V, E, and W Bands up to 110 GHz with an IF frequency of DC to 18 GHz. L and R ports support popular waveguide sizes from WR-28 to WR-10, and the IF port utilize Female SMA connectors.

WAVEGUIDE COUPLERS.....378

ASSEMBLIES.....383 *BROADWALL.....378* *CROSSGUIDE.....380*

Pasternack offers a brand new family of instrumentation grade directional waveguide couplers boasting accurate performance up to 110 GHz in seven popular frequency bands including K, Ka, Q, U, V, E and W bands. These waveguide couplers boast high directivity of 30 dB typical and insertion loss is as low as 0.6 dB in some models.



WAVEGUIDE DETECTORS..... 384



Waveguide detectors consists of 6 unique models covering a broad frequency range of 26.5 GHz to 110 GHz. The input ports use popular waveguide sizes ranging from WR-28 to WR-10, while the video output ports utilize SMA female connectors. The detector circuits use high performance GaAs Schottky Barrier Beam lead diodes with extremely low junction capacitance.

WG DIRECT READ ATTEN.....384

These continuously variable attenuators have “direct read” capability which allows the user to dial-in the amount of attenuation needed to within 2% accuracy over most of the attenuation range. The attenuation level is stable, highly repeatable and accurate across the full frequency and attenuation range. These attenuators are ideal for precision measurements in demanding applications like instrumentation and system calibration.



WAVEGUIDE ELECTROMECHANICAL RELAY SWITCHES.....384

Pasternack offers a series of 28 waveguide electromechanical relay switch models that offer full waveguide performance covering C, X, Ku, K and Ka frequency bands from 5.85 GHz 40 GHz. These switches re configured for single-pole double-throw (SPDT) operation with latching self-cut-off actuators, TTL logic and position indicators with manual override.



WG FIXED ATTENUATORS.....386



These waveguide fixed attenuator products offer precision attenuation levels over the operating frequency ranges.

FLEXIBLE WAVEGUIDES..... 386

This family of flexible seamless or twistable waveguides can be bent in both the E and H planes without impairing VSWR or attenuation.



WG FREQUENCY MULTIPLIERS.....388



Pasternack's family of Waveguide Frequency Multipliers have input frequency ranges from 12.5 to 20 GHz and output from 26.5 to 110 GHz.

WAVEGUIDE GUNN OSCILLATORS.....388

These Waveguide Gunn Oscillators consist of 2 models that have center frequencies of 24.125 GHz and 35 GHz.



WAVEGUIDE ISOLATORS..... 388



Pasternack Enterprises offers a wide variety of waveguide isolators from WR-10 to WR-112.

WG LOW NOISE AMPLIFIERS.....389

Pasternack WG Low Noise Amplifiers are ruggedly built 50 ohm designs and unconditionally stable with impressive performance across freq. bands.



WAVEGUIDE MAGIC TEES..... 389



Pasternack's magic, or hybrid tees are 4 port device that is internally tuned to optimize matching, balance, and isolation.

WG ORTHOMODE TRANSDUCERS.....389

These Orthomode Transducers are used for separating signals into two linear orthogonal signals. Pasternack's OMT line support from 8.2 to 90 GHz with 30-35 dB of isolation between ports.



WAVEGUIDE PHASE SHIFTERS.....390



These waveguide variable phase shifters are built using low loss dielectric material, which offers minimum insertion loss.

WAVEGUIDE POLARIZERS.....390



Waveguide Polarizers transform polarized signals from circular to linear and vice versa. They can operate as either right hand or left hand polarization. They currently cover Ku, Ka, and V bands.

WAVEGUIDE ROTARY JOINTS..... 390

Pasternack's waveguide rotary joints designed to perform in harsh operating environment. We offer L, U and Inline styles that support waveguide sizes from WR-28 to WR-75.



WAVEGUIDE SECTIONS..... 391



Pasternack offers a standard product line of waveguide straight section of various length and flanges, covering the frequency range from 5.85 GHz to 12.4 GHz.

WAVEGUIDE TERMINATIONS.....393

Pasternack has a large family of high performance loads from WR-112 to WR-10. These standard terminations can dissipate up to 300 Watts of power depending on the specific band.



WAVEGUIDE TRANSITIONS.....394



Pasternack's family of Waveguide Transitions/Adapters are used as a means of propagating RF/ Microwave energy from one waveguide size to another.

WAVEGUIDE TWISTS.....394

Pasternack offers waveguide twists in 45 degree left and right hand waveguide versions as well at 90 degree.



WAVEGUIDE VARIABLE ATTEN..... 395




The Continuously Variable attenuators are equipped with a micrometer, which enables rapid re-setting. With calibrated charts, attenuators can be used as direct reading attenuator for bench top test set use.

WG VOLTAGE VARIABLE ATTEN.....395

Pasternack's Waveguide Voltage Variable Attenuators operates across W, B, V, U and Ka Bands.



WAVEGUIDE ACCESSORIES.....396



Pasternack Enterprises offers a variety of waveguide accessories from WR-10 to WR-430.

WAVEGUIDE ANTENNAS

Waveguide Antennas With Coax Adapters






Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-28	26.5 - 40	10	WR-28 - 2.92mm Female	EAR99	PE9850B/2F-10	$2,090.00	$2,006.40	$1,922.80	$1,839.20	1
		10		EAR99	PEWAN028-10KF	$1,260.00	$1,209.60	$1,159.20	$1,108.80	2
		10	WR-28 - 2.92mm Male	EAR99	PEWAN028-10KM	$1,260.00	$1,209.60	$1,159.20	$1,108.80	3
		15	WR-28 - 2.92mm Female	EAR99	PEWAN028-15KF	$1,300.00	$1,248.00	$1,196.00	$1,144.00	4
		15		EAR99	PE9850B/2F-15	$2,170.00	$2,083.20	$1,996.40	$1,909.60	5
		15	WR-28 - 2.92mm Male	EAR99	PEWAN028-15KM	$1,300.00	$1,248.00	$1,196.00	$1,144.00	6
		20	WR-28 - 2.92mm Female	EAR99	PE9850B/2F-20	$2,310.00	$2,217.60	$2,125.20	$2,032.80	7
		20		EAR99	PEWAN028-20KF	$1,350.00	$1,296.00	$1,242.00	$1,188.00	8
		20	WR-28 - 2.92mm Male	EAR99	PEWAN028-20KM	$1,350.00	$1,296.00	$1,242.00	$1,188.00	9
WR-34	22 - 33	10	WR-34 - 2.92mm Female	EAR99	PE9851B/2F-10	$2,150.00	$2,064.00	$1,978.00	$1,892.00	10
		10		EAR99	PEWAN034-10KF	$1,270.00	$1,219.20	$1,168.40	$1,117.60	11
		15		EAR99	PE9851B/2F-15	$2,320.00	$2,227.20	$2,134.40	$2,041.60	12
		15		EAR99	PEWAN034-15KF	$1,310.00	$1,257.60	$1,205.20	$1,152.80	13
		20		EAR99	PE9851B/2F-20	$2,480.00	$2,380.80	$2,281.60	$2,182.40	14
		20		EAR99	PEWAN034-20KF	$1,360.00	$1,305.60	$1,251.20	$1,196.80	15
WR-42	18 - 26.5	10	WR-42 - 2.92mm Female	EAR99	PEWAN042-10ELKF	$1,400.00	$1,344.00	$1,288.00	$1,232.00	16
		10		EAR99	PEWAN042-10KF	$1,280.00	$1,228.80	$1,177.60	$1,126.40	17
		10	WR-42 - SMA Female	EAR99	PEWAN042-10SF	$1,280.00	$1,228.80	$1,177.60	$1,126.40	18
		10	WR-42 - 2.92mm Female	EAR99	PE9852B/2F-10	$1,870.00	$1,795.20	$1,720.40	$1,645.60	19
		15		EAR99	PE9852B/2F-15	$1,980.00	$1,900.80	$1,821.60	$1,742.40	20
		15		EAR99	PEWAN042-15ELKF	$1,470.00	$1,411.20	$1,352.40	$1,293.60	21
		15		EAR99	PEWAN042-15KF	$1,320.00	$1,267.20	$1,214.40	$1,161.60	22
		15	WR-42 - SMA Female	EAR99	PEWAN042-15SF	$1,320.00	$1,267.20	$1,214.40	$1,161.60	23
		20	WR-42 - 2.92mm Female	EAR99	PE9852B/2F-20	$2,130.00	$2,044.80	$1,959.60	$1,874.40	24
		20		EAR99	PEWAN042-20ELKF	$1,490.00	$1,430.40	$1,370.80	$1,311.20	25
		20		EAR99	PEWAN042-20KF	$1,400.00	$1,344.00	$1,288.00	$1,232.00	26
		20	WR-42 - SMA Female	EAR99	PEWAN042-20SF	$1,400.00	$1,344.00	$1,288.00	$1,232.00	27
WR-51	15 - 22	10	WR-51 - SMA Female	EAR99	PE9853B/SF-10	$1,900.00	$1,824.00	$1,748.00	$1,672.00	28
		10		EAR99	PEWAN051-10SF	$1,310.00	$1,257.60	$1,205.20	$1,152.80	29
		15		EAR99	PE9853B/SF-15	$2,030.00	$1,948.80	$1,867.60	$1,786.40	30
		15		EAR99	PEWAN051-15SF	$1,350.00	$1,296.00	$1,242.00	$1,188.00	31
		20		EAR99	PE9853B/SF-20	$2,120.00	$2,035.20	$1,950.40	$1,865.60	32
		20		EAR99	PEWAN051-20SF	$1,410.00	$1,353.60	$1,297.20	$1,240.80	33
WR-62	12.4 - 18	10	WR-62 - N Female	EAR99	PEWAN062-10NF	$1,120.00	$1,075.20	$1,030.40	$985.60	34
		10	WR-62 - SMA Female	EAR99	PEWAN062-10ELSF	$1,120.00	$1,075.20	$1,030.40	$985.60	35
		10		EAR99	PEWAN062-10SF	$1,120.00	$1,075.20	$1,030.40	$985.60	36
		10	WR-62 - SMA Male	EAR99	PEWAN062-10SM	$1,120.00	$1,075.20	$1,030.40	$985.60	37
		15	WR-62 - N Female	EAR99	PE9854B/NF-15	$1,690.00	$1,622.40	$1,554.80	$1,487.20	38
		15		EAR99	PEWAN062-15NF	$1,190.00	$1,142.40	$1,094.80	$1,047.20	39
		15	WR-62 - SMA Female	EAR99	PE9854B/SF-15	$1,690.00	$1,622.40	$1,554.80	$1,487.20	40
		15		EAR99	PEWAN062-15ELSF	$1,190.00	$1,142.40	$1,094.80	$1,047.20	41
		15		EAR99	PEWAN062-15SF	$1,190.00	$1,142.40	$1,094.80	$1,047.20	42
		15	WR-62 - SMA Male	EAR99	PEWAN062-15SM	$1,190.00	$1,142.40	$1,094.80	$1,047.20	43
		20	WR-62 - N Female	EAR99	PE9854B/NF-20	$1,800.00	$1,728.00	$1,656.00	$1,584.00	44
		20		EAR99	PEWAN062-20NF	$1,230.00	$1,180.80	$1,131.60	$1,082.40	45
		20	WR-62 - SMA Female	EAR99	PE9854B/SF-20	$1,790.00	$1,718.40	$1,646.80	$1,575.20	46
		20		EAR99	PEWAN062-20ELSF	$1,230.00	$1,180.80	$1,131.60	$1,082.40	47
		20		EAR99	PEWAN062-20SF	$1,230.00	$1,180.80	$1,131.60	$1,082.40	48
		20	WR-62 - SMA Male	EAR99	PEWAN062-20SM	$1,230.00	$1,180.80	$1,131.60	$1,082.40	49


Waveguide Antennas With Coax Adapters






Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-62	12.4 - 18	10	WR-62 - N Female	EAR99	PE9854B/NF-10	$1,630.00	$1,564.80	$1,499.60	$1,434.40	50
		10	WR-62 - SMA Female	EAR99	PE9854B/SF-10	$1,630.00	$1,564.80	$1,499.60	$1,434.40	51
WR-75	10 - 15	10	WR-75 - N Female	EAR99	PE9855B/NF-10	$1,660.00	$1,593.60	$1,527.20	$1,460.80	52
		10		EAR99	PEWAN075-10NF	$1,110.00	$1,065.60	$1,021.20	$976.80	53
		10	WR-75 - SMA Female	EAR99	PE9855B/SF-10	$1,630.00	$1,564.80	$1,499.60	$1,434.40	54
		10		EAR99	PEWAN075-10ELSF	$1,110.00	$1,065.60	$1,021.20	$976.80	55
		10		EAR99	PEWAN075-10SF	$1,110.00	$1,065.60	$1,021.20	$976.80	56
		15	WR-75 - N Female	EAR99	PE9855B/NF-15	$1,680.00	$1,612.80	$1,545.60	$1,478.40	57
		15		EAR99	PEWAN075-15NF	$1,150.00	$1,104.00	$1,058.00	$1,012.00	58
		15	WR-75 - SMA Female	EAR99	PE9855B/SF-15	$1,680.00	$1,612.80	$1,545.60	$1,478.40	59
		15		EAR99	PEWAN075-15ELSF	$1,150.00	$1,104.00	$1,058.00	$1,012.00	60
		15		EAR99	PEWAN075-15SF	$1,150.00	$1,104.00	$1,058.00	$1,012.00	61
		20		EAR99	PEWAN075-20NF	$1,190.00	$1,142.40	$1,094.80	$1,047.20	62
		20		EAR99	PE9855B/NF-20	$1,750.00	$1,680.00	$1,610.00	$1,540.00	63
		20	WR-75 - SMA Female	EAR99	PEWAN075-20ELSF	$1,190.00	$1,142.40	$1,094.80	$1,047.20	64
		20		EAR99	PEWAN075-20SF	$1,190.00	$1,142.40	$1,094.80	$1,047.20	65
		20		EAR99	PE9855B/SF-20	$1,750.00	$1,680.00	$1,610.00	$1,540.00	66
WR-90	8.2 - 12.4	10	WR-90 - N Female	EAR99	PE9856B/NF-10	$1,550.00	$1,488.00	$1,426.00	$1,364.00	67
		10	WR-90 - SMA Female	EAR99	PEWAN090-10ELSF	$1,260.00	$1,209.60	$1,159.20	$1,108.80	68
		10		EAR99	PEWAN090-10SF	$1,100.00	$1,056.00	$1,012.00	$968.00	69
		10		EAR99	PE9856B/SF-10	$1,490.00	$1,430.40	$1,370.80	$1,311.20	70
		15	WR-90 - N Female	EAR99	PE9856B/NF-15	$1,660.00	$1,593.60	$1,527.20	$1,460.80	71
		15	WR-90 - SMA Female	EAR99	PE9856B/SF-15	$1,660.00	$1,593.60	$1,527.20	$1,460.80	72
		15		EAR99	PEWAN090-15ELSF	$1,290.00	$1,238.40	$1,186.80	$1,135.20	73
		15		EAR99	PEWAN090-15SF	$1,130.00	$1,084.80	$1,039.60	$994.40	74
		20	WR-90 - N Female	EAR99	PE9856B/NF-20	$1,730.00	$1,660.80	$1,591.60	$1,522.40	75
		20	WR-90 - SMA Female	EAR99	PE9856B/SF-20	$1,740.00	$1,670.40	$1,600.80	$1,531.20	76
		20		EAR99	PEWAN090-20ELSF	$1,400.00	$1,344.00	$1,288.00	$1,232.00	77
		20		EAR99	PEWAN090-20SF	$1,170.00	$1,123.20	$1,076.40	$1,029.60	78
WR-102	7 - 11	10	WR-102 - N Female	EAR99	PE9857B/NF-10	$1,740.00	$1,670.40	$1,600.80	$1,531.20	79
		10	WR-102 - SMA Female	EAR99	PE9857B/SF-10	$1,800.00	$1,728.00	$1,656.00	$1,584.00	80
		10		EAR99	PEWAN102-10ELSF	$1,100.00	$1,056.00	$1,012.00	$968.00	81
		10		EAR99	PEWAN102-10SF	$1,100.00	$1,056.00	$1,012.00	$968.00	82
		15	WR-102 - N Female	EAR99	PE9857B/NF-15	$1,860.00	$1,785.60	$1,711.20	$1,636.80	83
		15	WR-102 - SMA Female	EAR99	PE9857B/SF-15	$1,880.00	$1,804.80	$1,729.60	$1,654.40	84
		15		EAR99	PEWAN102-15SF	$1,170.00	$1,123.20	$1,076.40	$1,029.60	85
		20	WR-102 - N Female	EAR99	PE9857B/NF-20	$1,910.00	$1,833.60	$1,757.20	$1,680.80	86
		20	WR-102 - SMA Female	EAR99	PE9857B/SF-20	$1,980.00	$1,900.80	$1,821.60	$1,742.40	87

Waveguide Antennas With Coax Adapters







Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-102	7 - 11	20	WR-102 - SMA Female	EAR99	PEWAN102-20SF	$1,220.00	$1,171.20	$1,122.40	$1,073.60	88
WR-112	7.05 - 10	10	WR-112 - N Female	EAR99	PE9858B/NF-10	$1,700.00	$1,632.00	$1,564.00	$1,496.00	89
		10	WR-112 - SMA Female	EAR99	PE9858B/SF-10	$1,650.00	$1,584.00	$1,518.00	$1,452.00	90
		10		EAR99	PEWAN112-10SF	$1,110.00	$1,065.60	$1,021.20	$976.80	91
		15	WR-112 - N Female	EAR99	PE9858B/NF-15	$1,780.00	$1,708.80	$1,637.60	$1,566.40	92
		15	WR-112 - SMA Female	EAR99	PE9858B/SF-15	$1,760.00	$1,689.60	$1,619.20	$1,548.80	93
		15		EAR99	PEWAN112-15ELSF	$1,140.00	$1,094.40	$1,048.80	$1,003.20	94
		20	WR-112 - N Female	EAR99	PE9858B/NF-20	$1,910.00	$1,833.60	$1,757.20	$1,680.80	95
		20	WR-112 - SMA Female	EAR99	PE9858B/SF-20	$1,870.00	$1,795.20	$1,720.40	$1,645.60	96
WR-137	5.85 - 8.2	10	WR-137 - N Female	EAR99	PE9859B/NF-10	$1,820.00	$1,747.20	$1,674.40	$1,601.60	97
		10	WR-137 - SMA Female	EAR99	PE9859B/SF-10	$1,820.00	$1,747.20	$1,674.40	$1,601.60	98
		15	WR-137 - N Female	EAR99	PE9859B/NF-15	$1,890.00	$1,814.40	$1,738.80	$1,663.20	99
		15	WR-137 - SMA Female	EAR99	PE9859B/SF-15	$1,890.00	$1,814.40	$1,738.80	$1,663.20	1
		15		EAR99	PEWAN137-15SF	$1,150.00	$1,104.00	$1,058.00	$1,012.00	2
		20	WR-137 - N Female	EAR99	PE9859B/NF-20	$1,980.00	$1,900.80	$1,821.60	$1,742.40	3
		20	WR-137 - SMA Female	EAR99	PE9859B/SF-20	$1,980.00	$1,900.80	$1,821.60	$1,742.40	4
WR-159	4.9 - 7.05	10	WR-159 - N Female	EAR99	PE9860B/NF-10	$2,000.00	$1,920.00	$1,840.00	$1,760.00	5
		10	WR-159 - SMA Female	EAR99	PE9860B/SF-10	$2,020.00	$1,939.20	$1,858.40	$1,777.60	6
		15	WR-159 - N Female	EAR99	PE9860B/NF-15	$2,190.00	$2,102.40	$2,014.80	$1,927.20	7
		15	WR-159 - SMA Female	EAR99	PE9860B/SF-15	$2,180.00	$2,092.80	$2,005.60	$1,918.40	8
		15		EAR99	PEWAN159-15SF	$1,160.00	$1,113.60	$1,067.20	$1,020.80	9
		20	WR-159 - N Female	EAR99	PE9860B/NF-20	$2,240.00	$2,150.40	$2,060.80	$1,971.20	10
		20	WR-159 - SMA Female	EAR99	PE9860B/SF-20	$2,240.00	$2,150.40	$2,060.80	$1,971.20	11
		20		EAR99	PEWAN159-20SF	$1,210.00	$1,161.60	$1,113.20	$1,064.80	12
WR-187	3.95 - 5.85	10	WR-187 - N Female	EAR99	PE9861B/NF-10	$2,200.00	$2,112.00	$2,024.00	$1,936.00	13
		10		EAR99	PEWAN187-10NF	$1,130.00	$1,084.80	$1,039.60	$994.40	14
		10	WR-187 - SMA Female	EAR99	PE9861B/SF-10	$2,270.00	$2,179.20	$2,088.40	$1,997.60	15
		10		EAR99	PEWAN187-10SF	$1,130.00	$1,084.80	$1,039.60	$994.40	16
		15	WR-187 - N Female	EAR99	PE9861B/NF-15	$2,490.00	$2,390.40	$2,290.80	$2,191.20	17
		15		EAR99	PEWAN187-15NF	$1,170.00	$1,123.20	$1,076.40	$1,029.60	18
		15	WR-187 - SMA Female	EAR99	PE9861B/SF-15	$2,490.00	$2,390.40	$2,290.80	$2,191.20	19
		15		EAR99	PEWAN187-15SF	$1,170.00	$1,123.20	$1,076.40	$1,029.60	20
		20	WR-187 - N Female	EAR99	PE9861B/NF-20	$2,650.00	$2,544.00	$2,438.00	$2,332.00	21
		20		EAR99	PEWAN187-20NF	$1,210.00	$1,161.60	$1,113.20	$1,064.80	22
		20	WR-187 - SMA Female	EAR99	PE9861B/SF-20	$2,650.00	$2,544.00	$2,438.00	$2,332.00	23
		20		EAR99	PEWAN187-20SF	$1,210.00	$1,161.60	$1,113.20	$1,064.80	24
WR-229	3.3 - 4.9	10	WR-229 - N Female	EAR99	PE9862B/NF-10	$2,190.00	$2,102.40	$2,014.80	$1,927.20	25
		10		EAR99	PEWAN229-10NF	$1,310.00	$1,257.60	$1,205.20	$1,152.80	26
		10	WR-229 - SMA Female	EAR99	PE9862B/SF-10	$2,190.00	$2,102.40	$2,014.80	$1,927.20	27
		10		EAR99	PEWAN229-10SF	$1,310.00	$1,257.60	$1,205.20	$1,152.80	28
		15	WR-229 - N Female	EAR99	PE9862B/NF-15	$2,500.00	$2,400.00	$2,300.00	$2,200.00	29
		15		EAR99	PEWAN229-15NF	$1,500.00	$1,440.00	$1,380.00	$1,320.00	30
		15	WR-229 - SMA Female	EAR99	PE9862B/SF-15	$2,520.00	$2,419.20	$2,318.40	$2,217.60	31

Waveguide Antennas With Coax Adapters





Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-229	3.3 - 4.9	15	WR-229 - SMA Female	EAR99	PEWAN229-15SF	$1,500.00	$1,440.00	$1,380.00	$1,320.00	32
		20	WR-229 - N Female	EAR99	PE9862B/NF-20	$2,770.00	$2,659.20	$2,548.40	$2,437.60	33
		20		EAR99	PEWAN229-20NF	$1,930.00	$1,852.80	$1,775.60	$1,698.40	34
		20	WR-229 - SMA Female	EAR99	PE9862B/SF-20	$2,820.00	$2,707.20	$2,594.40	$2,481.60	35
		20		EAR99	PEWAN229-20SF	$2,000.00	$1,920.00	$1,840.00	$1,760.00	36
WR-284	2.6 - 3.95	10	WR-284 - N Female	EAR99	PE9863B/NF-10	$2,940.00	$2,822.40	$2,704.80	$2,587.20	37
		10		EAR99	PEWAN284-10NF	$1,780.00	$1,708.80	$1,637.60	$1,566.40	38
		10	WR-284 - SMA Female	EAR99	PE9863B/SF-10	$3,310.00	$3,177.60	$3,045.20	$2,912.80	39
		10		EAR99	PEWAN284-10SF	$1,780.00	$1,708.80	$1,637.60	$1,566.40	40
		15	WR-284 - N Female	EAR99	PE9863B/NF-15	$3,230.00	$3,100.80	$2,971.60	$2,842.40	41
		15		EAR99	PEWAN284-15NF	$2,030.00	$1,948.80	$1,867.60	$1,786.40	42
		15	WR-284 - SMA Female	EAR99	PE9863B/SF-15	$3,430.00	$3,292.80	$3,155.60	$3,018.40	43
		15		EAR99	PEWAN284-15SF	$2,580.00	$2,476.80	$2,373.60	$2,270.40	44
		20	WR-284 - N Female	EAR99	PE9863B/NF-20	$3,820.00	$3,667.20	$3,514.40	$3,361.60	45
		20		EAR99	PEWAN284-20NF	$2,580.00	$2,476.80	$2,373.60	$2,270.40	46
		20	WR-284 - SMA Female	EAR99	PE9863B/SF-20	$4,030.00	$3,868.80	$3,707.60	$3,546.40	47
		20		EAR99	PEWAN284-20SF	$2,860.00	$2,745.60	$2,631.20	$2,516.80	48
WR-430	1.7 - 2.6	10	WR-430 - N Female	EAR99	PEWAN430-10NF	$2,420.00	$2,323.20	$2,226.40	$2,129.60	49
		10		EAR99	PE9864B/NF-10	$3,590.00	$3,446.40	$3,302.80	$3,159.20	50
		10	WR-430 - SMA Female	EAR99	PE9864B/SF-10	$3,560.00	$3,417.60	$3,275.20	$3,132.80	51
		10		EAR99	PEWAN430-10SF	$2,420.00	$2,323.20	$2,226.40	$2,129.60	52
		15	WR-430 - N Female	EAR99	PE9864B/NF-15	$4,550.00	$4,368.00	$4,186.00	$4,004.00	53
		15		EAR99	PEWAN430-15NF	$2,760.00	$2,649.60	$2,539.20	$2,428.80	54
		15	WR-430 - SMA Female	EAR99	PE9864B/SF-15	$4,700.00	$4,512.00	$4,324.00	$4,136.00	55
		15		EAR99	PEWAN430-15SF	$2,760.00	$2,649.60	$2,539.20	$2,428.80	56
		20	WR-430 - N Female	EAR99	PE9864B/NF-20	$6,380.00	$6,124.80	$5,869.60	$5,614.40	57
		20		EAR99	PEWAN430-20NF	$4,270.00	$4,099.20	$3,928.40	$3,757.60	58
		20	WR-430 - SMA Female	EAR99	PE9864B/SF-20	$6,250.00	$6,000.00	$5,750.00	$5,500.00	59
		20		EAR99	PEWAN430-20SF	$4,270.00	$4,099.20	$3,928.40	$3,757.60	60

Rectangular Gain Horn





Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-5	140 - 220	10	Round Cover UG-387/U-Mod	EAR99	PEWAN1029	$2,520.00	$2,431.80	$2,343.60	$2,268.00	61
		15		EAR99	PEWAN1030	$2,520.00	$2,431.80	$2,343.60	$2,268.00	62
		20		EAR99	PEWAN1031	$2,520.00	$2,431.80	$2,343.60	$2,268.00	63
		25		EAR99	PEWAN1032	$2,640.00	$2,547.60	$2,455.20	$2,376.00	64
WR-6	110 - 170	10		EAR99	PEWAN1025	$2,060.00	$1,987.90	$1,915.80	$1,854.00	65
		15		EAR99	PEWAN1026	$2,090.00	$2,016.85	$1,943.70	$1,881.00	66
		20		EAR99	PEWAN1027	$2,120.00	$2,045.80	$1,971.60	$1,908.00	67
		25		EAR99	PEWAN1028	$2,500.00	$2,412.50	$2,325.00	$2,250.00	68
WR-8	90 - 140	10		EAR99	PEWAN1021	$1,760.00	$1,698.40	$1,636.80	$1,584.00	69
		15		EAR99	PEWAN1022	$1,790.00	$1,727.35	$1,664.70	$1,611.00	70
		20		EAR99	PEWAN1023	$1,820.00	$1,756.30	$1,692.60	$1,638.00	71
		25		EAR99	PEWAN1024	$2,290.00	$2,209.85	$2,129.70	$2,061.00	72
WR-10	75 - 110	10		EAR99	PEWAN1017	$1,470.00	$1,418.55	$1,367.10	$1,323.00	73
		15		EAR99	PEWAN1018	$1,480.00	$1,428.20	$1,376.40	$1,332.00	74
		20		EAR99	PEWAN1019	$1,600.00	$1,544.00	$1,488.00	$1,440.00	75
		25		EAR99	PEWAN1020	$2,020.00	$1,949.30	$1,878.60	$1,818.00	76
WR-12	60 - 90	10		EAR99	PEWAN1013	$1,530.00	$1,476.45	$1,422.90	$1,377.00	77
		15		EAR99	PEWAN1014	$1,560.00	$1,505.40	$1,450.80	$1,404.00	78
		20		EAR99	PEWAN1015	$1,600.00	$1,544.00	$1,488.00	$1,440.00	79
		25	Round Cover UG-387/U	EAR99	PEWAN1016	$2,090.00	$2,016.85	$1,943.70	$1,881.00	80
WR-15	50 - 75	10	Round Cover UG-385/U-Mod	EAR99	PEWAN1009	$1,470.00	$1,418.55	$1,367.10	$1,323.00	81
		15		EAR99	PEWAN1010	$1,560.00	$1,505.40	$1,450.80	$1,404.00	82
		20		EAR99	PEWAN1011	$1,510.00	$1,457.15	$1,404.30	$1,359.00	83

Rectangular Gain Horn






Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-15	50 - 75	24	Round Cover UG-385/U	EAR99	PE9881-24	$1,840.00		84
		25	Round Cover UG-385/U-Mod	EAR99	PEWAN1012	$2,090.00		85
WR-19	40 - 60	10	Round Cover UG-383/U-Mod	EAR99	PEWAN1005	$1,610.00		86
		15		EAR99	PEWAN1006	$1,680.00		87
		20		EAR99	PEWAN1007	$1,710.00		88
		25		EAR99	PEWAN1008	$2,020.00		89
WR-28	26.5 - 40	10	Square Cover UG-599/U	EAR99	PE9850B-10	$1,060.00		90
		10		EAR99	PEWAN028-10	$865.00		91
		15		EAR99	PE9850-15	$1,290.00		92
		15		EAR99	PE9850B-15	$1,270.00		93
		15		EAR99	PEWAN028-15	$1,040.00		94
		20		EAR99	PE9850B-20	$1,200.00		95
		20		EAR99	PEWAN028-20	$975.00		96
WR-34	22 - 33	10	Square Cover UG-1530/U	EAR99	PE9851B-10	$1,030.00		97
		10		EAR99	PEWAN034-10	$880.00		98
		15		EAR99	PE9851B-15	$1,180.00		99
		15		EAR99	PEWAN034-15	$965.00		1
		20		EAR99	PE9851B-20	$1,340.00	See Web for Volume Pricing	2
		20		EAR99	PEWAN034-20	$1,090.00		3
WR-42	18 - 26.5	10	Square Cover UG-597/U	EAR99	PE9852B-10	$1,030.00		4
		10		EAR99	PEWAN042-10	$900.00		5
		15		EAR99	PE9852B-15	$1,190.00		6
		15		EAR99	PEWAN042-15	$970.00		7
		20		EAR99	PE9852B-20	$1,340.00		8
		20		EAR99	PEWAN042-20	$1,090.00		9
WR-51	15 - 22	10	Square Cover	EAR99	PEWAN051-10	$915.00		10
		10		EAR99	PE9853B-10	$925.00		11
		15		EAR99	PEWAN051-15	$960.00		12
		15		EAR99	PE9853B-15	$995.00		13
		20		EAR99	PEWAN051-20	$1,010.00		14
		20		EAR99	PE9853B-20	$1,050.00		15
WR-62	12.4 - 18	10		EAR99	PEWAN062-10	$935.00		16
		10	Square Cover UG-1665/U	EAR99	PE9854B-10	$1,050.00		17
		15	Square Cover	EAR99	PEWAN062-15	$980.00		18
		15		EAR99	PE9854B-15	$1,100.00		19
		20		EAR99	PEWAN062-20	$1,050.00		20
		20		EAR99	PE9854B-20	$1,290.00		21
WR-75	10 - 15	10		EAR99	PEWAN075-10	$955.00		22
		10		EAR99	PE9855B-10	$1,090.00		23
		15		EAR99	PEWAN075-15	$1,000.00		24
		15		EAR99	PE9855B-15	$1,150.00	See Web for Volume Pricing	25
		20		EAR99	PEWAN075-20	$1,050.00		26
		20		EAR99	PE9855B-20	$1,160.00		27
WR-90	8.2 - 12.4	10	Square Cover UG-135/U	EAR99	PE9856B-10	$1,040.00		28
		10		EAR99	PEWAN090-10	$955.00		29
		15		EAR99	PE9856B-15	$1,210.00		30
		15		EAR99	PEWAN090-15	$1,010.00		31
		20		EAR99	PE9856B-20	$1,270.00		32
		20		EAR99	PEWAN090-20	$1,060.00		33
WR-102	7 - 11	10	Square Cover	EAR99	PEWAN102-10	$890.00		34
		10	Square Cover UG-1493/U	EAR99	PE9857B-10	$1,030.00		35
		15	Square Cover	EAR99	PEWAN102-15	$935.00		36
		15		EAR99	PE9857B-15	$1,040.00		37
		20		EAR99	PEWAN102-20	$980.00		38
		20	Square Cover UG-1493/U	EAR99	PE9857B-20	$1,100.00		39
WR-112	7.05 - 10	10	Square Cover	EAR99	PEWAN112-10	$1,010.00		40
		10		EAR99	PE9858B-10	$1,130.00		41
		15		EAR99	PEWAN112-15	$1,060.00		42
		15	Square Cover UG-138/U	EAR99	PE9858B-15	$1,220.00		43
		20	Square Cover	EAR99	PEWAN112-20	$1,120.00		44

Rectangular Gain Horn






Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-112	7.05 - 10	20	Square Cover	EAR99	PE9858B-20	$1,300.00		45
WR-137	5.85 - 8.2	10	CMR-137	EAR99	PEWAN137-10	$970.00		46
		10		EAR99	PE9859B-10	$1,060.00		47
		15		EAR99	PEWAN137-15	$1,020.00		48
		15		EAR99	PE9859B-15	$1,130.00		49
		20		EAR99	PEWAN137-20	$1,070.00		50
		20	CMR-137F	EAR99	PE9859B-20	$1,220.00		51
WR-159	4.9 - 7.05	10	CMR-159	EAR99	PEWAN159-10	$1,020.00		52
		10		EAR99	PE9860B-10	$1,120.00		53
		15	Square Cover UG-1731/U	EAR99	PEWAN159-15	$1,070.00		54
		15	CMR-159	EAR99	PE9860B-15	$1,200.00		55
		20		EAR99	PEWAN159-20	$1,120.00		56
		20		EAR99	PE9860B-20	$1,220.00		57
WR-187	3.95 - 5.85	10	CMR-187	EAR99	PEWAN187-10	$1,080.00		58
		10		EAR99	PE9861B-10	$1,220.00		59
		15		EAR99	PEWAN187-15	$1,180.00		60
		15		EAR99	PE9861B-15	$1,450.00		61
		20		EAR99	PEWAN187-20	$1,350.00		62
		20		EAR99	PE9861B-20	$1,650.00		63
WR-229	3.3 - 4.9	10	CMR-229	EAR99	PEWAN229-10	$1,020.00		64
		10		EAR99	PE9862B-10	$1,240.00		65
		15		EAR99	PEWAN229-15	$1,260.00		66
		15		EAR99	PE9862B-15	$1,550.00		67
		20		EAR99	PEWAN229-20	$1,960.00		68
		20		EAR99	PE9862B-20	$1,940.00		69
WR-284	2.6 - 3.95	10	CMR-284	EAR99	PEWAN284-10	$1,290.00		70
		10	Round Cover UG-584/U	EAR99	PE9863B-10-U	$1,740.00		71
		10	CMR-284	EAR99	PE9863B-10	$1,640.00		72
		15		EAR99	PEWAN284-15	$1,870.00		73
		15	Round Cover UG-584/U	EAR99	PE9863B-15-U	$1,960.00		74
		15	CMR-284	EAR99	PE9863B-15	$2,080.00		75
		20		EAR99	PEWAN284-20	$2,220.00		76
		20	Round Cover UG-584/U	EAR99	PE9863B-20-U	$2,180.00		77
		20	CMR-284	EAR99	PE9863B-20	$2,640.00		78
WR-430	1.7 - 2.6	10	CPR-430F	EAR99	PEWAN430-10	$1,690.00		79
		10		EAR99	PE9864B-10	$2,080.00		80
		15		EAR99	PEWAN430-15	$2,300.00		81
		15		EAR99	PE9864B-15	$2,820.00		82
		20		EAR99	PEWAN430-20	$3,940.00		83
		20		EAR99	PE9864B-20	$4,840.00		84

See Web for Volume Pricing

See Web for Volume Pricing

Conical Gain Horn




Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-5	140 - 220	10	Round Cover UG-387/U	EAR99	PEWAN1065	$2,460.00	$2,373.90	$2,287.80	$2,214.00	85
		15		EAR99	PEWAN1066	$2,490.00	$2,402.85	$2,315.70	$2,241.00	86
		20		EAR99	PEWAN1067	$2,520.00	$2,431.80	$2,343.60	$2,268.00	87
		25		EAR99	PEWAN1068	$2,750.00	$2,653.75	$2,557.50	$2,475.00	88

Conical Gain Horn






Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
WR-6	100 - 112	10	Round Cover UG-387/U-Mod	EAR99	PEWAN1061	$2,060.00				89
		15		EAR99	PEWAN1062	$2,090.00				90
		20		EAR99	PEWAN1063	$2,120.00				91
		25		EAR99	PEWAN1064	$2,370.00				92
WR-8		10		EAR99	PEWAN1057	$1,480.00				93
		15		EAR99	PEWAN1058	$1,510.00				94
		20		EAR99	PEWAN1059	$1,680.00				95
		25		EAR99	PEWAN1060	$1,990.00				96
WR-10	87 - 100	10	Round Cover UG-387/U	EAR99	PEWAN1049	$1,480.00				97
		15		EAR99	PEWAN1050	$1,510.00				98
		20		EAR99	PEWAN1051	$1,680.00				99
		25		EAR99	PEWAN1052	$2,020.00				1
	77 - 87	10		EAR99	PEWAN1053	$1,480.00				2
		15		EAR99	PEWAN1054	$1,510.00				3
		20		EAR99	PEWAN1055	$1,680.00				4
		25		EAR99	PEWAN1056	$1,990.00				5
WR-12		10		EAR99	PEWAN1045	$1,480.00				6
		15		EAR99	PEWAN1046	$1,510.00				7
		20		EAR99	PEWAN1047	$1,680.00				8
		25		EAR99	PEWAN1048	$1,990.00				9
	68 - 77	10		EAR99	PEWAN1041	$1,480.00				10
		15		EAR99	PEWAN1042	$1,510.00				11
		20		EAR99	PEWAN1043	$1,680.00				12
		25		EAR99	PEWAN1044	$1,990.00				13
WR-15	58 - 68	10	Round Cover UG-385/U	EAR99	PEWAN1037	$1,480.00				14
		15		EAR99	PEWAN1038	$1,540.00				15
		20		EAR99	PEWAN1039	$1,680.00				16
		25		EAR99	PEWAN1040	$1,990.00				17
WR-19	50 - 58	10	Round Cover UG-383/U-Mod	EAR99	PEWAN1033	$1,350.00				18
		15		EAR99	PEWAN1034	$1,510.00				19
		20		EAR99	PEWAN1035	$1,680.00				20
		25		EAR99	PEWAN1036	$2,020.00				21

Wide Angle Scalar Feed Horn




Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-10	89 - 99	10	Round Cover UG-385/U-Mod	EAR99	PEWAN1073	$5,770.00	$5,568.05	$5,366.10	$5,193.00	22
		10		EAR99	PEWAN1074	$4,060.00	$3,917.90	$3,775.80	$3,654.00	23
WR-12	72 - 82	10	Round Cover UG-385/U	EAR99	PEWAN1071	$5,850.00	$5,645.25	$5,440.50	$5,265.00	24
		10		EAR99	PEWAN1072	$4,060.00	$3,917.90	$3,775.80	$3,654.00	25
WR-15	55 - 65	10		EAR99	PEWAN1069	$5,770.00	$5,568.05	$5,366.10	$5,193.00	26
		10		EAR99	PEWAN1070	$4,280.00	$4,130.20	$3,980.40	$3,852.00	27

Lens Gain Horn



Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1-24	25-49	50-99	100+	ROW
WR-10	88 - 100	40	Round Cover UG-387/U-Mod	EAR99	PEWAN1101	$11,425.00	$10,625.25	$9,825.50	$9,140.00	28
		48	Square Cover UG-387/U-Mod	EAR99	PEWAN1102	$11,725.00	$10,904.25	$10,083.50	$9,380.00	29
	89 - 99	34	Round Cover UG-387/U	EAR99	PEWAN1083	$5,770.00	$5,366.10	$4,962.20	$4,616.00	30

Lens Gain Horn




Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
WR-10	89 - 99	34	Round Cover UG-387/U	EAR99	PEWAN1085	$7,050.00				31
		40		EAR99	PEWAN1084	$6,290.00				32
		40		EAR99	PEWAN1086	$7,470.00				33
WR-12	72 - 82	32		EAR99	PEWAN1079	$4,910.00				34
		32		EAR99	PEWAN1081	$6,190.00				35
		37		EAR99	PEWAN1080	$5,340.00				36
		37		EAR99	PEWAN1082	$6,620.00				37
WR-15	55 - 65	32	Round Cover UG-385/U	EAR99	PEWAN1075	$3,630.00				38
		32		EAR99	PEWAN1077	$4,910.00				39
		37		EAR99	PEWAN1076	$4,060.00				40
		37		EAR99	PEWAN1078	$5,340.00				41

Omni-Directional





Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-10	89 - 99	2	Round Cover UG-387/U	EAR99	PEWAN1089	$8,450.00	$8,154.25	$7,858.50	$7,605.00	42
	90 - 100	0	Round Cover UG-387/U-Mod	EAR99	PEWAN1135	$5,640.00	$5,442.60	$5,245.20	$5,076.00	43
		6.5	Square Cover UG-387/U-Mod	EAR99	PEWAN1136	$5,640.00	$5,442.60	$5,245.20	$5,076.00	44
WR-12	75 - 79	2	Round Cover UG-387/U	EAR99	PEWAN1088	$8,330.00	$8,038.45	$7,746.90	$7,497.00	45
	71 - 86	2		EAR99	PEWAN1134	$5,340.00	$5,153.10	$4,966.20	$4,806.00	46
WR-15	58 - 62	3.5	Round Cover UG-385/U	EAR99	PEWAN1087	$8,450.00	$8,154.25	$7,858.50	$7,605.00	47
WR-28	26.5 - 40	7.5	Square Cover UG-599/U	EAR99	PEWAN1133	$4,730.00	$4,564.45	$4,398.90	$4,257.00	48

Probe Waveguide Antennas




Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-6	110 - 170	6.5	Round Cover UG-387/U-Mod	EAR99	PEWAN1124	$2,140.00	$2,065.10	$1,990.20	$1,926.00	49
WR-8	90 - 140	6.5		EAR99	PEWAN1125	$2,110.00	$2,036.15	$1,962.30	$1,899.00	50
WR-10	75 - 110	6.5		EAR99	PEWAN1126	$2,110.00	$2,036.15	$1,962.30	$1,899.00	51
WR-12	60 - 90	6.5	Round Cover UG-387/U	EAR99	PEWAN1127	$2,140.00	$2,065.10	$1,990.20	$1,926.00	52
WR-15	50 - 75	6.5	Round Cover UG-385/U	EAR99	PEWAN1128	$2,110.00	$2,036.15	$1,962.30	$1,899.00	53
WR-19	40 - 60	6.5	Round Cover UG-383/U-Mod	EAR99	PEWAN1129	$2,110.00	$2,036.15	$1,962.30	$1,899.00	54
WR-22	33 - 50	6.5	Round Cover UG-383/U	EAR99	PEWAN1130	$2,110.00	$2,036.15	$1,962.30	$1,899.00	55
WR-28	26.5 - 40	6.5	Square Cover UG-599/U	EAR99	PEWAN1131	$2,140.00	$2,065.10	$1,990.20	$1,926.00	56
WR-34	22 - 33	6.5	Square Cover UG-1530/U	EAR99	PEWAN1132	$2,140.00	$2,065.10	$1,990.20	$1,926.00	57

Sector Waveguide Antennas



Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-28	30 - 40	0	Square Cover UG-599/U-Mod	EAR99	PEWAN1144	$3,910.00	$3,773.15	$3,636.30	$3,519.00	58
	27.5 - 29.5	6	Square Cover UG-599/U	EAR99	PEWAN1143	$3,970.00	$3,831.05	$3,692.10	$3,573.00	59

Dual Polarized Scalar Feed Horn






Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
Circular	100 - 112	17	Round Cover UG-387/U-Mod	EAR99	PEWAN1109	$6,250.00	$6,031.25	$5,812.50	$5,625.00	60
	87 - 100	17	UG-387/U-Mod	EAR99	PEWAN1123	$5,640.00	$5,442.60	$5,245.20	$5,076.00	61
	77 - 87	17		EAR99	PEWAN1122	$5,490.00	$5,297.85	$5,105.70	$4,941.00	62
WR-10	75 - 110	13		EAR99	PEWAN1121	$23,025.00	$22,219.13	$21,413.25	$20,722.50	63
		15	Square Cover UG-387/U-Mod	EAR99	PEWAN1137	$10,525.00	$10,156.63	$9,788.25	$9,472.50	64
		20		EAR99	PEWAN1141	$10,525.00	$10,156.63	$9,788.25	$9,472.50	65
Circular	68 - 77	17	UG-387/U-Mod	EAR99	PEWAN1120	$5,490.00	$5,297.85	$5,105.70	$4,941.00	66
WR-12	60 - 90	13	UG-387/U	EAR99	PEWAN1119	$22,425.00	$21,640.13	$20,855.25	$20,182.50	67
		15	Square Cover UG-387/U	EAR99	PEWAN1138	$9,910.00	$9,563.15	$9,216.30	$8,919.00	68
Circular	58 - 68	17	UG-385/U-Mod	EAR99	PEWAN1118	$5,340.00	$5,153.10	$4,966.20	$4,806.00	69
WR-15	50 - 75	13		EAR99	PEWAN1117	$23,025.00	$22,219.13	$21,413.25	$20,722.50	70
WR-12		15	Square Cover UG-385/U	EAR99	PEWAN1139	$9,150.00	$8,829.75	$8,509.50	$8,235.00	71
WR-19	40 - 60	13	UG-383/U-Mod	EAR99	PEWAN1116	$18,750.00	$18,093.75	$17,437.50	$16,875.00	72
Circular	33 - 38.5	17	UG-599/U	EAR99	PEWAN1115	$4,880.00	$4,709.20	$4,538.40	$4,392.00	73
WR-22	33 - 50	15	Square Cover UG-383/U	EAR99	PEWAN1140	$8,540.00	$8,241.10	$7,942.20	$7,686.00	74
WR-28	26 - 30	17	UG-599/U	EAR99	PEWAN1113	$4,880.00	$4,709.20	$4,538.40	$4,392.00	75
Circular	26 - 33	17		EAR99	PEWAN1114	$4,880.00	$4,709.20	$4,538.40	$4,392.00	76
	24 - 33	16	Square Cover UG-1530/U	EAR99	PEWAN1110	$4,880.00	$4,709.20	$4,538.40	$4,392.00	77
WR-28	24 - 40	15	UG-599/U	EAR99	PEWAN1111	$14,250.00	$13,751.25	$13,252.50	$12,825.00	78
	24 - 42	10	Square Choke UG-599/U	EAR99	PEWAN1142	$12,200.00	$11,773.00	$11,346.00	$10,980.00	79
		15	UG-599/U	EAR99	PEWAN1112	$15,550.00	$15,005.75	$14,461.50	$13,995.00	80

Specialty Waveguide Antennas






Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
Broadband	1 - 18	11 dBi	SMA Connectors	EAR99	PE9887-11	$4,950.00	$4,776.75	$4,603.50	$4,455.00	81
			N Connectors	EAR99	PE9888-11	$4,670.00	$4,506.55	$4,343.10	$4,203.00	82
WR-15	50 - 75	42	Round Cover - UG-385/U	5A991	PE9881-42	$3,240.00	$3,110.40	$2,980.80	$2,851.20	83
		20		EAR99	PE9881A-20	$1,370.00	$1,315.20	$1,260.40	$1,205.60	84
		2 dBi		EAR99	PEW15A001	$4,940.00	$4,767.10	$4,594.20	$4,446.00	85
	56.5 - 67	34 dBi		5A991	PE9881-34	$1,960.00	$1,891.40	$1,822.80	$1,764.00	86

WAVEGUIDE ANTENNA ACCESSORIES

Waveguide to Coax Adapters





WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Flange Type	Connector	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-10	75-110	1	1.32:1	Round Cover UG-387/U-Mod	1.0mm Female	EAR99	PE-W10CA003	$6,110.00		87
			1.33:1		1.0mm Male	EAR99	PE-W10CA004	$6,020.00		88
WR-12	60-90		1.67:1	Round Cover UG-387/U	1.0mm Female	EAR99	PE-W12CA001	$6,010.00		89
					1.0mm Male	EAR99	PE-W12CA002	$5,910.00		90
WR-15	50-65	0.5	1.44:1	Round Cover UG-385/U	1.85mm Female	EAR99	PE-W15CA001	$1,760.00		91
					1.85mm Male	EAR99	PE-W15CA002	$1,810.00		92
WR-19	40-60	0.4	1.38:1	Round Cover UG-383/U-Mod	1.85mm Female	EAR99	PE-W19CA001	$1,890.00		93
					1.85mm Male	EAR99	PE-W19CA002	$1,800.00		94
WR-22	33-50		1.33:1	Round Cover UG-383/U	2.4mm Female	EAR99	PE-W22CA001	$1,960.00		95
					2.4mm Male	EAR99	PE-W22CA002	$1,630.00		96
			1.4:1		2.4mm Female	EAR99	PEW22CA100	$1,960.00		97
		0.5	1.6:1	UG383/U	2.4mm Female	EAR99	PEWCA1110	$1,770.00		98

See Web for Volume Pricing

Waveguide to Coax Adapters







WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Flange Type	Connector	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-28	26.5-40	0.3	1.25:1	Square Cover UG-599/U	2.92mm Female	EAR99	PEWCA1078	$900.00	See Web for Volume Pricing	99
				UBR320	2.92mm Female	EAR99	PEWCA1103	$1,180.00		1
			1.3:1	Square Cover UG-599/U	2.92mm Female	EAR99	PEWCA1020	$900.00		2
		0.35	1.29:1		2.92mm Male	EAR99	PE-W28CA002	$970.00		3
		0.4	1.25:1	UBR320	2.92mm Female	EAR99	PEWCA1104	$980.00		4
		0.5	1.3:1		2.92mm Female	EAR99	PEWCA1109	$1,280.00		5
			1.4:1	Square Cover	2.92mm Female	EAR99	PE9826	$600.00		6
			1.3:1	Square Cover UG-599/U	2.92mm Female	EAR99	PEWCA1000	$1,070.00		7
WR-34	21.7-33	0.3	1.35:1	UBR260	2.92mm Female	EAR99	PEWCA1102	$1,180.00		8
	22-33		1.25:1	Square Cover UG-1530/U	2.92mm Female	EAR99	PEWCA1021	$820.00		9
					2.92mm Female	EAR99	PEWCA1001	$885.00		10
			1.4:1	Square Cover	2.92mm Female	EAR99	PE9827	$950.00		11
WR-42	17.6-26.7	0.3	1.25:1	UBR220	2.92mm Female	EAR99	PEWCA1101	$1,180.00		12
		0.5			SMA Female	EAR99	PEWCA1100	$483.99		13
	18-26.5	0.3	1.29:1	Square Cover UG-597/U	2.92mm Female	EAR99	PE-W42CA001	$980.00		14
					2.92mm Male	EAR99	PE-W42CA002	$940.00		15
			1.3:1		SMA Female	EAR99	PEWCA1022	$715.00		16
		0.75	1.25:1		2.92mm Female	EAR99	PEWCA1019	$655.00		17
			1.03:1		SMA Female	EAR99	PEWCA1026	$825.00		18
			1.25:1	Square Cover UG-595/U	SMA Female	EAR99	PEWCA1018	$930.00		19
			1.3:1	Square Cover UG-597/U	2.92mm Female	EAR99	PEWCA1070	$1,090.00		20
			1.4:1	Square Cover	2.92mm Female	EAR99	PE9878	$760.00		21
				Square Cover UG-597/U	2.92mm Male	EAR99	PE9813A	$765.00		22
				Square Type	2.92mm Female	EAR99	PE9812	$550.00		23
WR-51	14.5-22	0.3	1.25:1	UBR180	SMA Female	EAR99	PEWCA1099	$555.00		24
	15-22			Square Cover	SMA Female	EAR99	PEWCA1002A	$660.00		25
					SMA Female	EAR99	PEWCA1027	$920.00		26
			1.3:1	Square Type	SMA Female	EAR99	PE9828	$755.00		27
					SMA Female	EAR99	PE9879	$950.00		28
WR-62	11.9-18	0.2	1.25:1	UBR140	N Female	EAR99	PEWCA1097	$483.99		29
					SMA Female	EAR99	PEWCA1098	$483.99		30
					SMA Female	EAR99	PEWCA1108	$545.00		31
	12.4-18	0.3		Square Cover UG-1665/U	SMA Female	EAR99	PEWCA1023	$675.00		32
			1.3:1	Square Type	SMA Female	EAR99	PE9803	$441.99		33
			1.2:1	Square Cover UG-1665/U	SMA Male	EAR99	PE9809	$435.99		34
			1.25:1		N Female	EAR99	PEWCA1028	$815.00		35
				Square Cover UG-419/U	SMA Female	EAR99	PEWCA1003	$625.00		36
			1.3:1	Square Cover UG-1665/U	N Female	EAR99	PEWCA1072	$1,060.00		37
					SMA Female	EAR99	PEWCA1071	$925.00		38
			1.4:1	Square Cover	N Male	EAR99	PE9806	$775.00		39
				Square Type	N Female	EAR99	PE9866	$840.00		40
					N Female	EAR99	PE9875	$423.99		41
					SMA Female	EAR99	PE9846	$720.00		42
WR-75	10-15	0.3	1.25:1	Square Cover	SMA Female	EAR99	PEWCA1024	$615.00		43
					N Female	EAR99	PEWCA1005	$835.00		44
					N Female	EAR99	PEWCA1029	$855.00		45
					SMA Female	EAR99	PEWCA1004	$765.00		46
			1.3:1		N Female	EAR99	PEWCA1074	$1,030.00		47
					SMA Female	EAR99	PEWCA1073	$925.00		48
				Square Type	N Female	EAR99	PE9874	$540.00		49
					SMA Female	EAR99	PE9819	$425.99		50
			1.4:1		N Female	EAR99	PE9867	$850.00		51
					SMA Female	EAR99	PE9847	$785.00		52
	9.84-15	0.2	1.25:1	UBR120	N Female	EAR99	PEWCA1095	$483.99		53
					SMA Female	EAR99	PEWCA1096	$483.99		54
WR-90	8.2-12.4			UBR100	N Female	EAR99	PEWCA1092	$483.99		55
					SMA Female	EAR99	PEWCA1093	$483.99		56
					SMA Female	EAR99	PEWCA1107	$545.00		57
		0.25		Square Cover UG-135/U	N Female	EAR99	PE9868	$970.00		58
		0.3			SMA Female	EAR99	PEWCA1025	$625.00		59
			1.3:1	Square Type	SMA Female	EAR99	PE9804	$463.99		60
			1.25:1	CMR-90	N Female	EAR99	PEWCA1033	$960.00		61
					SMA Female	EAR99	PEWCA1032	$960.00		62
				CPR-90G	N Female	EAR99	PEWCA1009	$705.00		63
					N Male	EAR99	PEWCA1035	$800.00		64
					N Female	EAR99	PEWCA1036	$865.00		65
					SMA Female	EAR99	PEWCA1007	$655.00		66
					SMA Female	EAR99	PEWCA1034	$800.00		67
				Square Cover UG-135/U	N Female	EAR99	PEWCA1031	$970.00		68

Waveguide to Coax Adapters







WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Flange Type	Connector	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-90	8.2-12.4		1.25:1	Square Cover UG-135/U	SMA Male	EAR99	PEWCA1030	$830.00		69
					SMA Female	EAR99	PEWCA1075	$950.00		70
				Square Cover UG-39/U	N Female	EAR99	PEWCA1008	$815.00		71
					SMA Female	EAR99	PEWCA1006	$785.00		72
			1.3:1	CPR-90G	N Female	EAR99	PE9873	$565.00		73
				Square Type	N Female	EAR99	PE9801	$545.00		74
					N Male	EAR99	PE9889	$555.00		75
					SMA Male	EAR99	PE9810	$540.00		76
			1.4:1		SMA Female	EAR99	PE9848	$695.00		77
WR-102	7-10		1.25:1	Square Cover UG-1493/U	SMA Female	EAR99	PEWCA1037	$895.00		78
	7-11			Square Cover	N Female	EAR99	PE9869	$555.00		79
				Square Cover UG-1493/U	N Female	EAR99	PEWCA1038	$960.00		80
					N Male	EAR99	PEWCA1039	$960.00		81
					SMA Female	EAR99	PE9805	$770.00		82
			1.3:1	Square Cover	SMA Male	EAR99	PE9811	$407.99		83
				Square Type	N Female	EAR99	PE9802	$575.00		84
					N Male	EAR99	PE9890	$565.00		85
			1.4:1		SMA Female	EAR99	PE9871	$540.00		86
WR-112	6.57-9.99	0.2	1.25:1	UBR84	N Female	EAR99	PEWCA1089	$491.99	See Web for Volume Pricing	87
					SMA Female	EAR99	PEWCA1090	$483.99		88
					SMA Female	EAR99	PEWCA1106	$590.00		89
	7.05-10			CMR-112	N Female	EAR99	PEWCA1043	$860.00		90
					SMA Female	EAR99	PEWCA1042	$825.00		91
				CPR-112G	N Female	EAR99	PEWCA1013	$685.00		92
					N Female	EAR99	PEWCA1045	$875.00		93
					SMA Female	EAR99	PEWCA1011	$805.00		94
					SMA Female	EAR99	PEWCA1044	$810.00		95
				Square Cover UG-138/U	N Female	EAR99	PEWCA1041	$810.00		96
					SMA Female	EAR99	PEWCA1040	$875.00		97
				Square Cover UG-51/U	N Female	EAR99	PEWCA1012	$915.00		98
					SMA Female	EAR99	PEWCA1010	$860.00		99
			1.3:1	CPR-112G	N Female	EAR99	PE9837	$740.00		1
				Square Type	N Female	EAR99	PE9820	$545.00		2
					N Female	EAR99	PE9870	$690.00		3
					SMA Female	EAR99	PE9884	$481.99		4
			1.4:1		SMA Female	EAR99	PE9865	$745.00		5
WR-137	5.38-8.17	0.2	1.25:1	PDR70	N Female	EAR99	PEWCA1087	$570.00		6
				UDR70	N Female	EAR99	PEWCA1086	$510.00		7
					SMA Female	EAR99	PEWCA1088	$457.99		8
	5.85-8.2	0.4	1.3:1	CMR-137	SMA Female	EAR99	PE9830	$625.00		9
			1.25:1		N Female	EAR99	PEWCA1049	$850.00		10
					SMA Female	EAR99	PEWCA1048	$835.00		11
				CPR-137G	N Female	EAR99	PEWCA1017	$700.00		12
					N Female	EAR99	PEWCA1051	$885.00		13
					SMA Female	EAR99	PEWCA1015	$725.00		14
					SMA Female	EAR99	PEWCA1050	$850.00		15
				Round Cover UG-344/U	N Female	EAR99	PEWCA1016	Call	See Web for Volume Pricing	16
					SMA Female	EAR99	PEWCA1014	$725.00		17
				Round Cover UG-441/U	N Female	EAR99	PEWCA1047	$885.00		18
					SMA Female	EAR99	PEWCA1046	$850.00		19
			1.3:1	CMR-137	N Female	EAR99	PE9876	$265.99		20
				CPR-137G	N Female	EAR99	PE9838	$437.99		21
WR-159	4.9-7.05		1.25:1	CMR-159	N Female	EAR99	PEWCA1053	$780.00		22
					SMA Female	EAR99	PEWCA1052	$840.00		23
				CPR-159G	N Female	EAR99	PEWCA1055	$780.00		24
					SMA Female	EAR99	PEWCA1054	$810.00		25
			1.3:1	CMR-159	N Female	EAR99	PE9821	$845.00		26
					SMA Female	EAR99	PE9831	$780.00		27
				CPR-159G	N Female	EAR99	PE9839	$945.00		28
	5.38-8.17	0.2	1.25:1	UDR58	SMA Female	EAR99	PEWCA1085	$555.00		29
WR-187	3.94-5.99			PDR48	N Female	EAR99	PEWCA1084	$610.00		30
				UDR48	N Female	EAR99	PEWCA1083	$570.00		31
					N Female	EAR99	PEWCA1105	$640.00		32
					SMA Female	EAR99	PEWCA1076	$505.00		33
	3.95-5.85			CMR-187	N Female	EAR99	PEWCA1058	$675.00		34
					SMA Female	EAR99	PEWCA1057	$775.00		35
				CPR-187G	N Female	EAR99	PEWCA1059	$675.00		36
				Round Cover UG-407/U	N Female	EAR99	PEWCA1056	$820.00		37
			1.3:1	CMR-187	N Female	EAR99	PE9822	$570.00		38

Waveguide to Coax Adapters






WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Flange Type	Connector	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-187	3.95-5.85		1.3:1	CMR-187	SMA Female	EAR99	PE9832	$1,090.00		39
				CPR-187G	N Female	EAR99	PE9840	$1,060.00		40
WR-229	3.3-4.9		1.25:1	CMR-229	N Female	EAR99	PEWCA1060	$800.00		41
				CPR-229G	N Female	EAR99	PEWCA1062	$800.00		42
					SMA Female	EAR99	PEWCA1061	$820.00		43
			1.3:1	CMR-229	N Female	EAR99	PE9823	$730.00		44
					SMA Female	EAR99	PE9833	$830.00		45
				CPR-229G	N Female	EAR99	PE9877	$1,320.00		46
WR-284	2.6-3.95	0.2	1.25:1	UDR32	N Female	EAR99	PEWCA1081	$740.00		47
					SMA Female	EAR99	PEWCA1082	$740.00		48
				CMR-284	N Female	EAR99	PEWCA1064	$845.00		49
					SMA Female	EAR99	PE9834	$1,550.00		50
				CPR-284G	N Female	EAR99	PEWCA1065	$970.00		51
				Round Cover UG-584/U	N Female	EAR99	PEWCA1063	$1,200.00		52
			1.3:1	CMR-284	N Female	EAR99	PE9824	$935.00		53
				CPR-284G	N Female	EAR99	PE9842	$665.00		54
WR-340	2.17-3.3	0.2	1.25:1	UDR26	N Female	EAR99	PEWCA1077	$755.00		55
	2.2-3.3			CPR-340F	N Female	EAR99	PEWCA1066	$1,630.00		56
				CPR-340G	N Female	EAR99	PEWCA1067	$1,600.00		57
WR-430	1.7-2.6			CPR-430F	N Female	EAR99	PEWCA1068	$1,820.00		58
				CPR-430G	N Female	EAR99	PEWCA1069	$1,880.00		59
			1.3:1	CPR-430F	N Female	EAR99	PE9872	$1,780.00		60
					SMA Female	EAR99	PE9835	$1,750.00		61
				CPR-430G	N Female	EAR99	PE9843	$1,860.00		62
	1.72-2.61	0.2	1.25:1	UDR22	N Female	EAR99	PEWCA1079	$1,380.00		63
		0.3			SMA Female	EAR99	PEWCA1080	$1,290.00		64

See Web for Volume Pricing

Double Ridge Waveguide to Coax Adapters






WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Flange Type	Connector	ECCN	Model No	1-4	5-9	10-24	25+	ROW
WRD-180	18-40	0.5	1.6:1	Square Cover UG	2.92mm Female	EAR99	PEWCA1120	$1,700.00	$1,615.00	$1,530.00	$1,462.00	65
				Square Cover	2.92mm Female	EAR99	PEWCA1115	$1,440.00	$1,368.00	$1,296.00	$1,238.40	66
WRD-650	6.5-18		1.5:1	Square Cover UG	N Female	EAR99	PEWCA1111	$1,050.00	$997.50	$945.00	$903.00	67
					N Female	EAR99	PEWCA1116	$1,530.00	$1,453.50	$1,377.00	$1,315.80	68
					SMA Female	EAR99	PEWCA1112	$1,110.00	$1,054.50	$999.00	$954.60	69
					SMA Female	EAR99	PEWCA1117	$1,530.00	$1,453.50	$1,377.00	$1,315.80	70
WRD-750	7.5-18				N Female	EAR99	PEWCA1113	$1,230.00	$1,168.50	$1,107.00	$1,057.80	71
					N Female	EAR99	PEWCA1118	$1,530.00	$1,453.50	$1,377.00	$1,315.80	72
					SMA Female	EAR99	PEWCA1114	$1,380.00	$1,311.00	$1,242.00	$1,186.80	73
					SMA Female	EAR99	PEWCA1119	$1,530.00	$1,453.50	$1,377.00	$1,315.80	74

Corner Reflectors



Description	Model No	1	2-4	5-9	10+	ROW
1.4 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0000	$1,110.00	$1,071.15	$1,032.30	$999.00	75
1.8 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0001	$1,220.00	$1,177.30	$1,134.60	$1,098.00	76
2.4 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0002	$1,330.00	$1,283.45	$1,236.90	$1,197.00	77
3.2 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0003	$1,870.00	$1,804.55	$1,739.10	$1,683.00	78

Corner Reflectors



Description	Model No	1	2-4	5-9	10+	ROW
4.3 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0004	$1,840.00	$1,775.60	$1,711.20	$1,656.00	79
6 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0005	$2,190.00	$2,113.35	$2,036.70	$1,971.00	80
8 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0006	$2,600.00	$2,509.00	$2,418.00	$2,340.00	81
8.5 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0007	$2,980.00	$2,875.70	$2,771.40	$2,682.00	82
8.9 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0008	$3,330.00	$3,213.45	$3,096.90	$2,997.00	83
10 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0009	$3,960.00	$3,821.40	$3,682.80	$3,564.00	84
13 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0010	$4,640.00	$4,477.60	$4,315.20	$4,176.00	85
13.5 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0011	$5,220.00	$5,037.30	$4,854.60	$4,698.00	86
16 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0012	$7,590.00	$7,324.35	$7,058.70	$6,831.00	87
24 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0013	$10,450.00	$10,084.25	$9,718.50	$9,405.00	88

WAVEGUIDE BANDPASS FILTERS





Waveguide Type	RF Frequency (GHz.)	Max VSWR	Flange Type	ECCN	Model No	1-9	10-24	25-49	10+	ROW
WR-28	30 - 31	1.4:1	Square Cover	EAR99	PE-W28F001	$695.00	$660.25	$625.50	$597.70	89
	38 - 40	1.5:1		EAR99	PE-W28F002	$473.99	$450.29	$426.59	$407.63	90
WR-42	20.2 - 21.2	1.5:1		EAR99	PE-W42F001	$471.99	$448.39	$424.79	$405.91	91
	24.25 - 24.45	1.5:1		EAR99	PE-W42F004	$459.99	$436.99	$413.99	$395.59	92
		1.8:1		EAR99	PE-W42F002	$439.99	$422.39	$409.19	$400.39	93

WAVEGUIDE BENDS




Waveguide Type	RF Frequency (GHz.)	Insertion Loss (dB)	Bend Plane	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-5	140 - 220		E-Bend	Round Cover UG-383/U-Mod	EAR99	PEW5B0000	$675.00	See Web for Volume Pricing	95
			H-Bend		EAR99	PEW5B0001	$700.00		96
WR-6	110 - 170	0.35	E-Bend		EAR99	PEW6B0000	$635.00		97
			H-Bend		EAR99	PEW6B0001	$635.00		98
WR-8	90 - 140	0.3	E-Bend		EAR99	PEW8B0000	$635.00		99
			H-Bend		EAR99	PEW8B0001	$630.00		1
WR-10	75 - 110	0.21	E-Bend	Round Cover UG-387/U-Mod	EAR99	PE-W10B001	$620.00		2
WR-12	60 - 90	0.3	E-Bend	Round Cover UG-387/U	EAR99	PE-W12B001	$525.00		4
		0.21	H-Bend		EAR99	PE-W12B002	$510.00		5
WR-15	50 - 75	0.17	E-Bend	Round Cover UG-385/U	EAR99	PE-W15B001	$755.00		6
			H-Bend		EAR99	PE-W15B002	$690.00		7
WR-19	40 - 60	0.18		Round Cover UG-383/U-Mod	EAR99	PE-W19B002	$495.99		8
WR-22	33 - 50	0.25		Round Cover UG-383/U	EAR99	PEW22B100	$469.99		9
			E-Bend		EAR99	PEW22B101	$469.99		10
		0.16			EAR99	PE-W22B001	$495.99		11

WAVEGUIDE BENDS






Waveguide Type	RF Frequency (GHz.)	Insertion Loss (dB)	Bend Plane	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-28	26.5 - 40	0.28	H-Bend	Square Cover UG-599/U	EAR99	PE-W28B002	$660.00		12
		0.3	E-Bend		EAR99	PE-W28B003	$550.00		13
WR-42	18 - 26.5	0.15	H-Bend	Square Cover UG-595/U	EAR99	PEW42B100	$510.00		14
		0.2	E-Bend		EAR99	PEW42B101	$525.00		15
WR-51	15 - 22	0.09		UBR180	EAR99	PE-W51B001	$481.99		16
WR-62	12.4 - 18	0.15		Square Cover UG-419/U	EAR99	PE-W62B001	$483.99		17
			H-Bend		EAR99	PE-W62B002	$590.00		18
		0.09	E-Bend		EAR99	PE-W62B003	$635.00		19
			H-Bend		EAR99	PE-W62B004	$520.00		20
WR-75	10 - 15	0.15	E-Bend	UBR120	EAR99	PE-W75B001	$545.00		21
			H-Bend		EAR99	PE-W75B002	$590.00		22
WR-90	8.2 - 12.4		E-Bend	Square Cover UG-39/U	EAR99	PE-W90B001	$499.99		23
			H-Bend		EAR99	PE-W90B002	$510.00		24
			E-Bend	CPR-90G	EAR99	PE-W90B003A	$500.00		25
			H-Bend		EAR99	PE-W90B004A	$437.99		26
WR-112	7.05 - 10		E-Bend	Square Cover UG-51/U	EAR99	PE-W112B001	$880.00		27
			H-Bend		EAR99	PE-W112B002	$615.00		28
WR-137	5.85 - 8.2		H-Bend	Round Cover UG-344/U	EAR99	PE-W137B002	$555.00		30
			E-Bend	CPR-137G	EAR99	PE-W137B003A	$650.00		31
			H-Bend		EAR99	PE-W137B004	$785.00		32
WRD-180	18 - 40	0.4	E-Bend	Square Cover UG	EAR99	PEWRD180B001	$875.00		33
			H-Bend		EAR99	PEWRD180B002	$875.00		34
WRD-650	6.5 - 18		E-Bend		EAR99	PEWRD650B001	$780.00		35
			H-Bend		EAR99	PEWRD650B002	$780.00		36
WRD-750	7.5 - 18		E-Bend		EAR99	PEWRD750B001	$780.00		37
			H-Bend		EAR99	PEWRD750B002	$780.00		38

See Web for Volume Pricing

WAVEGUIDE BULKHEAD ADAPTERS






Frequency Range (GHz.)	Waveguide Size	Flange 1	Flange 2	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
75.0 - 110.0	WR-10	Round Cover UG-387/U-Mod	Round Cover UG-387/U-Mod	PEWAD5000	$1,270.00		39
60.0 - 90.0	WR-12	Round Cover UG-387/U	Round Cover UG-387/U	PEWAD5001	$1,150.00		40
50.0 - 75.0	WR-15	Round Cover UG-385/U	Round Cover UG-385/U	PEWAD5002	$1,150.00		41
33.0 - 50.0	WR-22	Round Cover UG-383/U	Round Cover UG-383/U	PEWAD5007A	$1,050.00		43
26.5 - 40.0	WR-28	Square Cover UG-599/U	Square Cover UG-599/U	PEWAD5008	$915.00		45
			Square Cover UG-599/U	PEWAD5005	$1,280.00		46
22.0 - 33.0	WR-34	Square Cover UG-1530/U	Square Cover UG-1530/U	PEWAD5009	$870.00		47
18.0 - 26.5	WR-42	Square Cover UG-595/U	Square Cover UG-595/U	PEWAD5010	$955.00		48
			Square Cover UG-595/U	PEWAD5006	$1,280.00		49
15.0 - 22.0	WR-51	Square Cover	Square Cover	PEWAD5011	$960.00		50
12.4 - 18.0	WR-62	Square Cover UG-1665/U	Square Cover UG-1665/U	PEWAD5012	$1,000.00		51
10.0 - 15.0	WR-75	Square Cover	Square Cover	PEWAD5013	$1,050.00		52
8.2 - 12.4	WR-90	Square Cover UG-39/U	Square Cover UG-39/U	PEWAD5014	$1,140.00		53
		CPR-90G	CPR-90G	PEWAD5015	$1,090.00		54
7.05 - 10.0	WR-112	Square Cover UG-51/U	Square Cover UG-51/U	PEWAD5016	$1,130.00		55
		CPR-112G	CPR-112G	PEWAD5017	$1,150.00		56
5.85 - 8.2	WR-137	Round Cover UG-344/U	Round Cover UG-344/U	PEWAD5018	$1,210.00		57
		CPR-137G	CPR-137G	PEWAD5019	$1,210.00		58

See Web for Volume Pricing

WAVEGUIDE CIRCULATORS




WG Type	Flange Type	RF Freq. Range (GHz)	Max. Input Power (Watts)	Max. VSWR	Min. Isolation (dB)	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-28	Cover	26.5 - 40	5	1.6:1	12	EAR99	PEWCR1005	$2,450.00	$2,352.00	$2,254.00	$2,156.00	59
WR-42		18 - 26.5		1.3:1	18	EAR99	PEWCR1004	$2,220.00	$2,131.20	$2,042.40	$1,953.60	60
WR-62		12.4 - 18	10	1.3:1	18	EAR99	PEWCR1003	$2,080.00	$1,996.80	$1,913.60	$1,830.40	61
WR-75		10 - 15		1.3:1	18	EAR99	PEWCR1002	$1,780.00	$1,708.80	$1,637.60	$1,566.40	62
WR-90		8.2 - 12.4	20	1.3:1	18	EAR99	PEWCR1001	$1,850.00	$1,776.00	$1,702.00	$1,628.00	63
WR-112		7.05 - 10		1.3:1	18	EAR99	PEWCR1000	$1,820.00	$1,747.20	$1,674.40	$1,601.60	64

WAVEGUIDE CONVERTER MIXERS

Down Converter



RF/LO Frequency (GHz.)	IF Frequency (GHz.)	LO Power (dBm)	Typ Conv. Loss (dB)	RF & LO Waveguide Type	IF Connector	ECCN	Model No	1	2-4	5-9	10+	ROW
26.5 - 40	DC - 18	15	6	WR-28 UG-599/U	SMA Female	EAR99	PE12D1005	$4,350.00	$4,176.00	$4,002.00	$3,828.00	65
33 - 50	DC - 18	15	7	WR-22 UG-383/U	SMA Female	EAR99	PE12D1004	$5,020.00	$4,819.20	$4,618.40	$4,417.60	66
50 - 75	DC - 18	15	8	WR-15 UG-385/U	SMA Female	EAR99	PE12D1002	$5,660.00	$5,433.60	$5,207.20	$4,980.80	67
60 - 90	DC - 18	15	9	WR-12 UG-387/U	SMA Female	EAR99	PE12D1001	$5,270.00	$5,059.20	$4,848.40	$4,637.60	68
75 - 110	DC - 18	15	9	WR-10 UG-387/U-Mod	SMA Female	EAR99	PE12D1000	$7,400.00	$7,104.00	$6,808.00	$6,512.00	69

Up Converter



RF/LO Frequency (GHz.)	IF Frequency (GHz.)	LO Power (dBm)	Typ Conv. Loss (dB)	RF & LO Waveguide Type	IF Connector	ECCN	Model No	1	2-4	5-9	10+	ROW
26.5 - 40	DC - 18	15	6	WR-28 UG-599/U	SMA Female	EAR99	PE13U1005	$4,710.00	$4,521.60	$4,333.20	$4,144.80	70
33 - 50	DC - 18	15	7	WR-22 UG-383/U	SMA Female	EAR99	PE13U1004	$5,700.00	$5,472.00	$5,244.00	$5,016.00	71
40 - 60	DC - 18	15	7	WR-19 UG-383/U	SMA Female	EAR99	PE13U1003	$5,900.00	$5,664.00	$5,428.00	$5,192.00	72
50 - 75	DC - 18	15	8	WR-15 UG-385/U	SMA Female	EAR99	PE13U1002	$6,790.00	$6,518.40	$6,246.80	$5,975.20	73
60 - 90	DC - 18	15	9	WR-12 UG-387/U	SMA Female	EAR99	PE13U1001	$6,290.00	$6,038.40	$5,786.80	$5,535.20	74
75 - 110	DC - 18	15	9	WR-10 UG-387/U	SMA Female	EAR99	PE13U1000	$6,330.00	$6,076.80	$5,823.60	$5,570.40	75

WAVEGUIDE COUPLERS

Broadwall




WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Coupling (dB)	Directivity (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-10	75 - 110	1.1	1.2:1	20	30	Round Cover UG-387/U-Mod	EAR99	PE-W10CP001-20	$2,910.00	$2,793.60	$2,677.20	$2,560.80	76
				20	30		EAR99	PE-W10CP003-20	$3,230.00	$3,100.80	$2,971.60	$2,842.40	77
		1.4		10	30		EAR99	PE-W10CP003-10	$3,230.00	$3,100.80	$2,971.60	$2,842.40	79
			1.1:1	20	40	Round Cover UG-387/U	EAR99	PEW10CP010-20	$3,070.00	$2,947.20	$2,824.40	$2,701.60	80

Broadwall







WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Coupling (dB)	Directivity (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-12	60 - 90	1	1.2:1	20	30	Round Cover UG-387/U	EAR99	PE-W12CP001-20	$3,100.00	$2,976.00	$2,852.00	$2,728.00	81
				20	30		EAR99	PE-W12CP003-20	$3,140.00	$3,014.40	$2,888.80	$2,763.20	82
		1.4		10	30		EAR99	PE-W12CP001-10	$3,100.00	$2,976.00	$2,852.00	$2,728.00	83
				10	30		EAR99	PE-W12CP003-10	$3,260.00	$3,129.60	$2,999.20	$2,868.80	84
WR-15	50 - 75	1	1.1:1	20	40	Round Cover UG-385/U	EAR99	PEWCP1080-20	$2,910.00	$2,793.60	$2,677.20	$2,560.80	85
			1.2:1	20	30		EAR99	PE-W15CP001-20	$3,020.00	$2,899.20	$2,778.40	$2,657.60	86
		1.4		10	30		EAR99	PE-W15CP001-10	$2,920.00	$2,803.20	$2,686.40	$2,569.60	87
				10	30		EAR99	PE-W15CP003-10	$2,920.00	$2,803.20	$2,686.40	$2,569.60	88
WR-19	40 - 60	0.8		10	30	Round Cover UG-383/U	EAR99	PE-W19CP003-10	$3,400.00	$3,264.00	$3,128.00	$2,992.00	89
				20	30		EAR99	PE-W19CP003-20	$3,340.00	$3,206.40	$3,072.80	$2,939.20	90
		1		20	30		EAR99	PE-W19CP001-20	$2,700.00	$2,592.00	$2,484.00	$2,376.00	91
WR-22	33 - 50	0.8	1.1:1	20	30		EAR99	PEW22CP010-20	$2,770.00	$2,659.20	$2,548.40	$2,437.60	93
			1.2:1	20	30		EAR99	PE-W22CP003-20	$3,040.00	$2,918.40	$2,796.80	$2,675.20	94
		1	1.05:1	10			EAR99	PEWCP1079-10	$2,880.00	$2,764.80	$2,649.60	$2,534.40	95
		1.2	1.2:1	10	30		EAR99	PE-W22CP001-10	$2,920.00	$2,803.20	$2,686.40	$2,569.60	96
WR-28	26.5 - 40	0.6	1.1:1	20	30	Square Cover UG-599/U	EAR99	PEW28CP010-20	$2,830.00	$2,716.80	$2,603.60	$2,490.40	97
		0.7	1.05:1	20	40		EAR99	PE-W28CP002-20	$2,830.00	$2,716.80	$2,603.60	$2,490.40	98
			1.2:1	10	30		EAR99	PE-W28CP003-10	$2,940.00	$2,822.40	$2,704.80	$2,587.20	99
		1		10	30		EAR99	PE-W28CP002-10	$2,830.00	$2,716.80	$2,603.60	$2,490.40	1
WR-34	22 - 33	0.15	1.05:1	20	35	Square Cover UG-1530/U	EAR99	PEWCP1006	$1,910.00	$1,833.60	$1,757.20	$1,680.80	2
				30	35		EAR99	PEWCP1007	$1,910.00	$1,833.60	$1,757.20	$1,680.80	3
		0.35		10	35		EAR99	PEWCP1005	$1,830.00	$1,756.80	$1,683.60	$1,610.40	4
WR-42	18 - 26.5	0.6	1.2:1	20	30	Square Cover UG-595/U	EAR99	PE-W42CP002-20	$2,830.00	$2,716.80	$2,603.60	$2,490.40	5
				20	30		EAR99	PE-W42CP004-20	$2,900.00	$2,784.00	$2,668.00	$2,552.00	6
		1		10	30		EAR99	PE-W42CP004-10	$2,900.00	$2,784.00	$2,668.00	$2,552.00	7
WR-51	15 - 22	0.15	1.05:1	10	35	Square Cover	EAR99	PEWCP1008	$1,870.00	$1,795.20	$1,720.40	$1,645.60	8
				20	35		EAR99	PEWCP1009	$1,870.00	$1,795.20	$1,720.40	$1,645.60	9
				30	35		EAR99	PEWCP1010	$1,940.00	$1,862.40	$1,784.80	$1,707.20	10
WR-62	12.4 - 18			10	40	Square Cover UG-419/U	EAR99	PEWCP1011	$1,900.00	$1,824.00	$1,748.00	$1,672.00	11
				20	40		EAR99	PEWCP1012	$1,740.00	$1,670.40	$1,600.80	$1,531.20	12
				30	40		EAR99	PEWCP1013	$1,740.00	$1,670.40	$1,600.80	$1,531.20	13
WR-75	10 - 15			10	40	Square Cover	EAR99	PEWCP1014	$1,610.00	$1,545.60	$1,481.20	$1,416.80	14
				30	40		EAR99	PEWCP1016	$1,760.00	$1,689.60	$1,619.20	$1,548.80	16
WR-90	8.2 - 12.4			10	40	Square Cover	EAR99	PEWCP1017	$2,140.00	$2,054.40	$1,968.80	$1,883.20	18
				20	40	Square Cover	EAR99	PEWCP1018	$1,880.00	$1,804.80	$1,729.60	$1,654.40	20
				30	40	CPR-90G	EAR99	PEWCP1022	$1,820.00	$1,747.20	$1,674.40	$1,601.60	21
				30	40	Square Cover	EAR99	PEWCP1019	$2,040.00	$1,958.40	$1,876.80	$1,795.20	22
WR-112	7.05 - 10			10	40	Square Cover	EAR99	PEWCP1023A	$1,740.00	$1,670.40	$1,600.80	$1,531.20	24
				30	40	Square Cover	EAR99	PEWCP1025	$1,730.00	$1,660.80	$1,591.60	$1,522.40	28
WR-137	5.85 - 8.2			10	40	CPR-137G	EAR99	PEWCP1032	$1,820.00	$1,747.20	$1,674.40	$1,601.60	29
				20	40	CPR-137G	EAR99	PEWCP1033	$1,800.00	$1,728.00	$1,656.00	$1,584.00	31
				30	40	CPR-137G	EAR99	PEWCP1034	$1,890.00	$1,814.40	$1,738.80	$1,663.20	33

Crossguide*






WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Coupling (dB)	Directivity (dB)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-34	22 - 33	0.1	1.05:1	20	20	Square Cover UG-1530/U	EAR99	PEWCP1035	$1,220.00	See Web for Volume Pricing	35
				30	20		EAR99	PEWCP1036	$1,390.00		36
				40	25		EAR99	PEWCP1037	$1,130.00		37
				50	10		EAR99	PEWCP1038	$1,220.00		38
WR-42	18 - 26.5			20	30	Square Cover UG-595/U	EAR99	PEWCP1039	$985.00		39
				30	20		EAR99	PEWCP1040	$1,070.00		40
				40	20		EAR99	PEWCP1041	$970.00		41
				50	10		EAR99	PEWCP1042	$1,070.00		42
WR-51	15 - 22			20	20	Square Cover	EAR99	PEWCP1043	$1,500.00		43
WR-62	12.4 - 18			20	20	Square Cover UG-419/U	EAR99	PEWCP1047	$920.00		47
				30	10		EAR99	PEWCP1048	$1,020.00		48
				40	30		EAR99	PEWCP1049	$970.00		49
				50	10		EAR99	PEWCP1050	$970.00		50
WR-75	10 - 15			20	25	Square Cover	EAR99	PEWCP1051	$1,020.00		51
				30	25		EAR99	PEWCP1052A	$1,010.00		52
				40	15		EAR99	PEWCP1053	$945.00		53
				50	10		EAR99	PEWCP1054	$975.00		54
WR-90	8.2 - 12.4			20	20	Square Cover UG-39/U	EAR99	PEWCP1055	$920.00		55
				20	25	CPR-90G	EAR99	PEWCP1059	$1,020.00		56
				30	20		EAR99	PEWCP1060	$1,020.00		57
				30	20	Square Cover UG-39/U	EAR99	PEWCP1056	$985.00		58
				40	10	Square Cover UG-39/U	EAR99	PEWCP1057	$1,050.00		60
				50	10	Square Cover UG-39/U	EAR99	PEWCP1058	$1,230.00		62
WR-112	7.05 - 10			20	25	CPR-112G	EAR99	PEWCP1067	$1,110.00		63
				20	45	Square Cover UG-51/U	EAR99	PEWCP1063	$1,110.00		64
				30	25	CPR-112G	EAR99	PEWCP1068	$1,120.00		65
				30	25	Square Cover UG-51/U	EAR99	PEWCP1064	$1,160.00		66
				40	20	CPR-112G	EAR99	PEWCP1069	$1,110.00		67
				40	20	Square Cover UG-51/U	EAR99	PEWCP1065	$1,020.00		68
				50	10	CPR-112G	EAR99	PEWCP1070	$1,210.00		69
				50	10	Square Cover UG-51/U	EAR99	PEWCP1066	$1,200.00		70
WR-137	5.85 - 8.2			20	20	CPR-137G	EAR99	PEWCP1075	$1,060.00		71
				20	25	Round Cover UG-344/U	EAR99	PEWCP1071	$1,110.00		72
				30	20	CPR-137G	EAR99	PEWCP1076	$1,080.00		73
				30	20	Round Cover UG-344/U	EAR99	PEWCP1072	$1,110.00		74
				40	20	CPR-137G	EAR99	PEWCP1077	$1,060.00		75
				40	20	Round Cover UG-344/U	EAR99	PEWCP1073	$1,110.00		76
				50	10	CPR-137G	EAR99	PEWCP1078	$1,060.00		77

*These WG crossguide couplers are available as assemblies with termination and/or with WG to Coax Adapters, see WG Coupler Asemblies or visit our website

Crossguide* with Termination






WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Coupling (dB)	Directivity (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-34	22 - 33	0.1	1.05:1	20	20	Square Cover UG-1530/U	EAR99	PEWCT1000	$1,920.00	$1,843.20	$1,766.40	$1,689.60	79
				30	20		EAR99	PEWCT1001	$1,920.00	$1,843.20	$1,766.40	$1,689.60	80
				40	25		EAR99	PEWCT1002	$2,020.00	$1,939.20	$1,858.40	$1,777.60	81
				50	10		EAR99	PEWCT1003	$1,920.00	$1,843.20	$1,766.40	$1,689.60	82
WR-42	18 - 26.5			20	30	Square Cover UG-595/U	EAR99	PEWCT1004	$1,630.00	$1,564.80	$1,499.60	$1,434.40	83
				30	20		EAR99	PEWCT1005	$1,630.00	$1,564.80	$1,499.60	$1,434.40	84
				40	20		EAR99	PEWCT1006	$1,630.00	$1,564.80	$1,499.60	$1,434.40	85
				50	10		EAR99	PEWCT1007	$1,630.00	$1,564.80	$1,499.60	$1,434.40	86
WR-51	15 - 22			20	20	Square Cover	EAR99	PEWCT1008	$2,180.00	$2,092.80	$2,005.60	$1,918.40	87
				30	30		EAR99	PEWCT1009	$2,180.00	$2,092.80	$2,005.60	$1,918.40	88
				40	30		EAR99	PEWCT1010	$2,180.00	$2,092.80	$2,005.60	$1,918.40	89
				50	10		EAR99	PEWCT1011	$2,180.00	$2,092.80	$2,005.60	$1,918.40	90
WR-62	12.4 - 18			20	20	Square Cover UG-419/U	EAR99	PEWCT1012	$1,620.00	$1,555.20	$1,490.40	$1,425.60	91
				30	10		EAR99	PEWCT1013	$1,700.00	$1,632.00	$1,564.00	$1,496.00	92
				40	30		EAR99	PEWCT1014	$1,620.00	$1,555.20	$1,490.40	$1,425.60	93
				50	10		EAR99	PEWCT1015	$1,620.00	$1,555.20	$1,490.40	$1,425.60	94
WR-75	10 - 15			20	25	Square Cover	EAR99	PEWCT1016	$1,720.00	$1,651.20	$1,582.40	$1,513.60	95
				30	25		EAR99	PEWCT1017	$1,630.00	$1,564.80	$1,499.60	$1,434.40	96
				40	15		EAR99	PEWCT1018	$1,630.00	$1,564.80	$1,499.60	$1,434.40	97
				50	10		EAR99	PEWCT1019	$1,720.00	$1,651.20	$1,582.40	$1,513.60	98
WR-90	8.2 - 12.4			20	20	Square Cover UG-39/U	EAR99	PEWCT1020	$1,590.00	$1,526.40	$1,462.80	$1,399.20	99
				20	25	CPR-90G	EAR99	PEWCT1024	$1,670.00	$1,603.20	$1,536.40	$1,469.60	1
				30	20		EAR99	PEWCT1025	$1,670.00	$1,603.20	$1,536.40	$1,469.60	2
				30	20	Square Cover UG-39/U	EAR99	PEWCT1021	$1,590.00	$1,526.40	$1,462.80	$1,399.20	3
				40	10	CPR-90G	EAR99	PEWCT1026	$1,670.00	$1,603.20	$1,536.40	$1,469.60	4
				40	10	Square Cover UG-39/U	EAR99	PEWCT1022	$1,590.00	$1,526.40	$1,462.80	$1,399.20	5
				50	10	CPR-90G	EAR99	PEWCT1027	$1,670.00	$1,603.20	$1,536.40	$1,469.60	6
				50	10	Square Cover UG-39/U	EAR99	PEWCT1023	$1,610.00	$1,545.60	$1,481.20	$1,416.80	7
WR-112	7.05 - 10			20	25	CPR-112G	EAR99	PEWCT1032	$1,790.00	$1,718.40	$1,646.80	$1,575.20	8
				20	45	Square Cover UG-51/U	EAR99	PEWCT1028	$1,770.00	$1,699.20	$1,628.40	$1,557.60	9
				30	25	CPR-112G	EAR99	PEWCT1033	$1,790.00	$1,718.40	$1,646.80	$1,575.20	10
				30	25	Square Cover UG-51/U	EAR99	PEWCT1029	$1,870.00	$1,795.20	$1,720.40	$1,645.60	11
				40	20	CPR-112G	EAR99	PEWCT1034	$1,790.00	$1,718.40	$1,646.80	$1,575.20	12
				40	20	Square Cover UG-51/U	EAR99	PEWCT1030	$1,770.00	$1,699.20	$1,628.40	$1,557.60	13
				50	10	CPR-112G	EAR99	PEWCT1035	$1,790.00	$1,718.40	$1,646.80	$1,575.20	14
				50	10	Square Cover UG-51/U	EAR99	PEWCT1031	$1,770.00	$1,699.20	$1,628.40	$1,557.60	15
WR-137	5.85 - 8.2			20	20	CPR-137G	EAR99	PEWCT1040	$1,780.00	$1,708.80	$1,637.60	$1,566.40	16
				20	25	Round Cover UG-344/U	EAR99	PEWCT1036	$1,830.00	$1,756.80	$1,683.60	$1,610.40	17
				30	20	CPR-137G	EAR99	PEWCT1041	$1,780.00	$1,708.80	$1,637.60	$1,566.40	18
				30	20	Round Cover UG-344/U	EAR99	PEWCT1037	$1,830.00	$1,756.80	$1,683.60	$1,610.40	19
				40	20	CPR-137G	EAR99	PEWCT1042	$1,780.00	$1,708.80	$1,637.60	$1,566.40	20
				40	20	Round Cover UG-344/U	EAR99	PEWCT1038	$1,830.00	$1,756.80	$1,683.60	$1,610.40	21
				50	10	CPR-137G	EAR99	PEWCT1043	$1,780.00	$1,708.80	$1,637.60	$1,566.40	22
				50	10	Round Cover UG-344/U	EAR99	PEWCT1039	$1,830.00	$1,756.80	$1,683.60	$1,610.40	23

*These WG crossguide couplers are available as assemblies with termination and/or with WG to Coax Adapters, see WG Coupler Asemblies or visit our website

Crossguide* with Termination and WG to Coax Adapter






WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Coupling (dB)	Directivity (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-34	22 - 33	0.1	1.05:1	20	20	Square Cover UG-1530/U	EAR99	PEWCT1044	$2,670.00	$2,563.20	$2,456.40	$2,349.60	24
				30	20		EAR99	PEWCT1045	$2,710.00	$2,601.60	$2,493.20	$2,384.80	25
				40	25		EAR99	PEWCT1046	$2,670.00	$2,563.20	$2,456.40	$2,349.60	26
				50	10		EAR99	PEWCT1047	$2,670.00	$2,563.20	$2,456.40	$2,349.60	27
WR-42	18 - 26.5			20	30	Square Cover UG-595/U	EAR99	PEWCT1048	$2,420.00	$2,323.20	$2,226.40	$2,129.60	28
				30	20		EAR99	PEWCT1049	$2,460.00	$2,361.60	$2,263.20	$2,164.80	29
				40	20		EAR99	PEWCT1050	$2,420.00	$2,323.20	$2,226.40	$2,129.60	30
				50	10		EAR99	PEWCT1051	$2,420.00	$2,323.20	$2,226.40	$2,129.60	31
WR-51	15 - 22			20	20	Square Cover	EAR99	PEWCT1052	$2,860.00	$2,745.60	$2,631.20	$2,516.80	32
				30	30		EAR99	PEWCT1053	$2,860.00	$2,745.60	$2,631.20	$2,516.80	33
				40	30		EAR99	PEWCT1054	$2,860.00	$2,745.60	$2,631.20	$2,516.80	34
				50	10		EAR99	PEWCT1055	$2,860.00	$2,745.60	$2,631.20	$2,516.80	35
WR-62	12.4 - 18			20	20	Square Cover UG-419/U	EAR99	PEWCT1056	$2,260.00	$2,169.60	$2,079.20	$1,988.80	36
				30	10		EAR99	PEWCT1057	$2,450.00	$2,352.00	$2,254.00	$2,156.00	37
				40	30		EAR99	PEWCT1058	$2,230.00	$2,140.80	$2,051.60	$1,962.40	38
				50	10		EAR99	PEWCT1059	$2,260.00	$2,169.60	$2,079.20	$1,988.80	39
WR-75	10 - 15			20	25	Square Cover	EAR99	PEWCT1060	$2,250.00	$2,160.00	$2,070.00	$1,980.00	40
				20	25		EAR99	PEWCT1064	$2,340.00	$2,246.40	$2,152.80	$2,059.20	41
				30	25		EAR99	PEWCT1061	$2,370.00	$2,275.20	$2,180.40	$2,085.60	42
				30	25		EAR99	PEWCT1065	$2,310.00	$2,217.60	$2,125.20	$2,032.80	43
				40	15		EAR99	PEWCT1062	$2,470.00	$2,371.20	$2,272.40	$2,173.60	44
				40	15		EAR99	PEWCT1066	$2,530.00	$2,428.80	$2,327.60	$2,226.40	45
				50	10		EAR99	PEWCT1063	$2,420.00	$2,323.20	$2,226.40	$2,129.60	46
				50	10		EAR99	PEWCT1067	$2,340.00	$2,246.40	$2,152.80	$2,059.20	47
WR-90	8.2 - 12.4			20	20	Square Cover UG-39/U	EAR99	PEWCT1068	$2,360.00	$2,265.60	$2,171.20	$2,076.80	48
				20	20		EAR99	PEWCT1076	$2,500.00	$2,400.00	$2,300.00	$2,200.00	49
				20	25	CPR-90G	EAR99	PEWCT1072	$2,310.00	$2,217.60	$2,125.20	$2,032.80	50
				20	25		EAR99	PEWCT1080	$2,400.00	$2,304.00	$2,208.00	$2,112.00	51
				30	20		EAR99	PEWCT1073	$2,310.00	$2,217.60	$2,125.20	$2,032.80	52
				30	20		EAR99	PEWCT1081	$2,360.00	$2,265.60	$2,171.20	$2,076.80	53
				30	20	Square Cover UG-39/U	EAR99	PEWCT1069	$2,360.00	$2,265.60	$2,171.20	$2,076.80	54
				30	20		EAR99	PEWCT1077	$2,280.00	$2,188.80	$2,097.60	$2,006.40	55
				40	10	CPR-90G	EAR99	PEWCT1074	$2,310.00	$2,217.60	$2,125.20	$2,032.80	56
				40	10		EAR99	PEWCT1082	$2,360.00	$2,265.60	$2,171.20	$2,076.80	57
				40	10	Square Cover UG-39/U	EAR99	PEWCT1070	$2,230.00	$2,140.80	$2,051.60	$1,962.40	58
				40	10		EAR99	PEWCT1078	$2,410.00	$2,313.60	$2,217.20	$2,120.80	59
				50	10	CPR-90G	EAR99	PEWCT1075	$2,310.00	$2,217.60	$2,125.20	$2,032.80	60
				50	10		EAR99	PEWCT1083	$2,360.00	$2,265.60	$2,171.20	$2,076.80	61
				50	10	Square Cover UG-39/U	EAR99	PEWCT1071	$2,230.00	$2,140.80	$2,051.60	$1,962.40	62
				50	10		EAR99	PEWCT1079	$2,410.00	$2,313.60	$2,217.20	$2,120.80	63
WR-112	7.05 - 10			20	25	CPR-112G	EAR99	PEWCT1088	$2,480.00	$2,380.80	$2,281.60	$2,182.40	64
				20	25		EAR99	PEWCT1096	$2,500.00	$2,400.00	$2,300.00	$2,200.00	65
				20	45	Square Cover UG-51/U	EAR99	PEWCT1084	$2,590.00	$2,486.40	$2,382.80	$2,279.20	66
				20	45		EAR99	PEWCT1092	$2,480.00	$2,380.80	$2,281.60	$2,182.40	67
				30	25	CPR-112G	EAR99	PEWCT1089	$2,480.00	$2,380.80	$2,281.60	$2,182.40	68
				30	25		EAR99	PEWCT1097	$2,500.00	$2,400.00	$2,300.00	$2,200.00	69
				30	25	Square Cover UG-51/U	EAR99	PEWCT1085	$2,460.00	$2,361.60	$2,263.20	$2,164.80	70
				30	25		EAR99	PEWCT1093	$2,480.00	$2,380.80	$2,281.60	$2,182.40	71
				40	20	CPR-112G	EAR99	PEWCT1090	$2,480.00	$2,380.80	$2,281.60	$2,182.40	72
				40	20		EAR99	PEWCT1098	$2,500.00	$2,400.00	$2,300.00	$2,200.00	73
				40	20	Square Cover UG-51/U	EAR99	PEWCT1086	$2,460.00	$2,361.60	$2,263.20	$2,164.80	74
				40	20		EAR99	PEWCT1094	$2,480.00	$2,380.80	$2,281.60	$2,182.40	75
				50	10	CPR-112G	EAR99	PEWCT1091	$2,480.00	$2,380.80	$2,281.60	$2,182.40	76
				50	10		EAR99	PEWCT1099	$2,740.00	$2,630.40	$2,520.80	$2,411.20	77
				50	10	Square Cover UG-51/U	EAR99	PEWCT1087	$2,460.00	$2,361.60	$2,263.20	$2,164.80	78
				50	10		EAR99	PEWCT1095	$2,480.00	$2,380.80	$2,281.60	$2,182.40	79
WR-137	5.85 - 8.2			20	20	CPR-137G	EAR99	PEWCT1104	$2,500.00	$2,400.00	$2,300.00	$2,200.00	80
				20	20		EAR99	PEWCT1112	$2,540.00	$2,438.40	$2,336.80	$2,235.20	81
				20	25	Round Cover UG-344/U	EAR99	PEWCT1100	$2,540.00	$2,438.40	$2,336.80	$2,235.20	82
				20	25		EAR99	PEWCT1108	$2,540.00	$2,438.40	$2,336.80	$2,235.20	83
				30	20	CPR-137G	EAR99	PEWCT1105	$2,530.00	$2,428.80	$2,327.60	$2,226.40	84
				30	20		EAR99	PEWCT1113	$2,500.00	$2,400.00	$2,300.00	$2,200.00	85

*These WG crossguide couplers are available as assemblies with termination and/or with WG to Coax Adapters, see WG Coupler Asemblies or visit our website

Crossguide* with Termination and WG to Coax Adapter





WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Coupling (dB)	Directivity (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-137	5.85 - 8.2	0.1	1.05:1	30	20	Round Cover UG-344/U	EAR99	PEWCT1101	$2,540.00	$2,438.40	$2,336.80	$2,235.20	86
				30	20		EAR99	PEWCT1109	$2,540.00	$2,438.40	$2,336.80	$2,235.20	87
				40	20	CPR-137G	EAR99	PEWCT1106	$2,500.00	$2,400.00	$2,300.00	$2,200.00	88
				40	20		EAR99	PEWCT1114	$2,740.00	$2,630.40	$2,520.80	$2,411.20	89
				40	20	Round Cover UG-344/U	EAR99	PEWCT1102	$2,540.00	$2,438.40	$2,336.80	$2,235.20	90
				40	20		EAR99	PEWCT1110	$2,680.00	$2,572.80	$2,465.60	$2,358.40	91
				50	10	CPR-137G	EAR99	PEWCT1107	$2,530.00	$2,428.80	$2,327.60	$2,226.40	92
				50	10		EAR99	PEWCT1115	$2,500.00	$2,400.00	$2,300.00	$2,200.00	93
				50	10	Round Cover UG-344/U	EAR99	PEWCT1103	$2,540.00	$2,438.40	$2,336.80	$2,235.20	94
				50	10		EAR99	PEWCT1111	$2,540.00	$2,438.40	$2,336.80	$2,235.20	95

*These WG crossguide couplers are available as assemblies with termination and/or with WG to Coax Adapters, see WG Coupler Asemblies or visit our website

WAVEGUIDE COUPLER ASSEMBLIES

WG Crossguide Coupler	WG Crossguide Coupler with Termination	WG Crossguide Coupler with Termination & Coax Adapter SMA/ Type N	Conn. Type
PEWCP1035	PEWCT1000	PEWCT1044	2.92mm
PEWCP1036	PEWCT1001	PEWCT1045	2.92mm
PEWCP1037	PEWCT1002	PEWCT1046	2.92mm
PEWCP1038	PEWCT1003	PEWCT1047	2.92mm
PEWCP1039	PEWCT1004	PEWCT1048	SMA
PEWCP1040	PEWCT1005	PEWCT1049	SMA
PEWCP1041	PEWCT1006	PEWCT1050	SMA
PEWCP1042	PEWCT1007	PEWCT1051	SMA
PEWCP1043	PEWCT1008	PEWCT1052	SMA
PEWCP1044	PEWCT1009	PEWCT1053	SMA
PEWCP1045	PEWCT1010	PEWCT1054	SMA
PEWCP1046	PEWCT1011	PEWCT1055	SMA
PEWCP1047	PEWCT1012	PEWCT1056	SMA
PEWCP1048	PEWCT1013	PEWCT1057	SMA
PEWCP1049	PEWCT1014	PEWCT1058	SMA
PEWCP1050	PEWCT1015	PEWCT1059	SMA
PEWCP1051	PEWCT1016	PEWCT1060	SMA
		PEWCT1064	N
PEWCP1052	PEWCT1017	PEWCT1061	SMA
		PEWCT1065	N
PEWCP1053	PEWCT1018	PEWCT1062	SMA
		PEWCT1066	N
PEWCP1054	PEWCT1019	PEWCT1063	SMA
		PEWCT1067	N
PEWCP1055	PEWCT1020	PEWCT1068	SMA
		PEWCT1076	N
PEWCP1056	PEWCT1021	PEWCT1069	SMA
		PEWCT1077	N
PEWCP1057	PEWCT1022	PEWCT1070	SMA
		PEWCT1078	N
PEWCP1058	PEWCT1023	PEWCT1071	SMA
		PEWCT1079	N
PEWCP1059	PEWCT1024	PEWCT1072	SMA
		PEWCT1080	N
PEWCP1060	PEWCT1025	PEWCT1073	SMA
		PEWCT1081	N

WG Crossguide Coupler	WG Crossguide Coupler with Termination	WG Crossguide Coupler with Termination & Coax Adapter SMA/ Type N	Conn. Type
PEWCP1061	PEWCT1026	PEWCT1074	SMA
		PEWCT1082	N
PEWCP1062	PEWCT1027	PEWCT1075	SMA
		PEWCT1083	N
PEWCP1063	PEWCT1028	PEWCT1084	SMA
		PEWCT1092	N
PEWCP1064	PEWCT1029	PEWCT1085	SMA
		PEWCT1093	N
PEWCP1065	PEWCT1030	PEWCT1086	SMA
		PEWCT1094	N
PEWCP1066	PEWCT1031	PEWCT1087	SMA
		PEWCT1095	N
PEWCP1067	PEWCT1032	PEWCT1088	SMA
		PEWCT1096	N
PEWCP1068	PEWCT1033	PEWCT1089	SMA
		PEWCT1097	N
PEWCP1069	PEWCT1034	PEWCT1090	SMA
		PEWCT1098	N
PEWCP1070	PEWCT1035	PEWCT1091	SMA
		PEWCT1099	N
PEWCP1071	PEWCT1036	PEWCT1100	SMA
		PEWCT1108	N
PEWCP1072	PEWCT1037	PEWCT1101	SMA
		PEWCT1109	N
PEWCP1073	PEWCT1038	PEWCT1102	SMA
		PEWCT1110	N
PEWCP1074	PEWCT1039	PEWCT1103	SMA
		PEWCT1111	N
PEWCP1075	PEWCT1040	PEWCT1104	SMA
		PEWCT1112	N
PEWCP1076	PEWCT1041	PEWCT1105	SMA
		PEWCT1113	N
PEWCP1077	PEWCT1042	PEWCT1106	SMA
		PEWCT1114	N
PEWCP1078	PEWCT1043	PEWCT1107	SMA
		PEWCT1115	N

WAVEGUIDE DETECTORS





Connector 1	RF Frequency (GHz.)	Voltage Sensitivity (V/nW)	Input Power (dBm)	Connector 2	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-28 UG-599/U	26.5 - 40	-1,000	20	SMA Female	EAR99	PE80T3005	$4,120.00	$3,955.20	$3,790.40	$3,625.60	1
WR-22 UG-383/U	33 - 50	-800		SMA Female	EAR99	PE80T3004	$4,970.00	$4,796.05	$4,622.10	$4,473.00	2
WR-15 UG-385/U	50 - 75	-700		SMA Female	EAR99	PE80T3002	$5,250.00	$5,040.00	$4,830.00	$4,620.00	4
WR-12 UG-387/U	60 - 90	-900		SMA Female	EAR99	PE80T3001	$5,050.00	$4,848.00	$4,646.00	$4,444.00	5
WR-10 UG-387/U	75 - 100	-900		SMA Female	EAR99	PE80T3000	$4,870.00	$4,675.20	$4,480.40	$4,285.60	6

WAVEGUIDE DIRECT READ ATTENUATORS





WG Type	RF Freq. (GHz.)	Max Atten (dB)	IL (dB)	Max VSWR	Input Power (Watts)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-10	75 - 110	50	1	1.2:1	0.2	Round Cover UG-387/U-Mod	EAR99	PE-W10AT5001	$6,460.00	$6,201.60	$5,943.20	$5,684.80	7
WR-12	60 - 90		0.9	1.2:1	0.2	Round Cover UG-387/U	EAR99	PE-W12AT5001	$7,080.00	$6,832.20	$6,584.40	$6,372.00	8
WR-15	50 - 75		0.8	1.2:1	0.3	Round Cover UG-385/U	EAR99	PE-W15AT5001	$6,810.00	$6,537.60	$6,265.20	$5,992.80	9
WR-22	33 - 50		0.6	1.15:1	0.4	Round Cover UG-383/U	EAR99	PE-W22AT5001	$6,710.00	$6,441.60	$6,173.20	$5,904.80	11
		60		1.15:1	0.5		EAR99	PE-W22AT5002	$6,460.00	$6,201.60	$5,943.20	$5,684.80	12
WR-28	26.5 - 40	50	0.5	1.15:1	0.5	Square Cover UG-599/U	EAR99	PE-W28AT5001	$6,330.00	$6,076.80	$5,823.60	$5,570.40	13
WR-42	18 - 26.5			1.15:1	1	Square Cover UG-595/U	EAR99	PE-W42AT5001	$7,080.00	$6,796.80	$6,513.60	$6,230.40	14

WAVEGUIDE ELECTROMECHANICAL RELAY SWITCHES





Features:
A: Absorptive
AR: Auto Reset
B: Break Before Make
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
M: Manual Override
N: Normally Open
NT: Non-Terminated
P: Pulse Latching
R: Reflective
RS: Reset
S: Self Cut Off
SI: Set Indicator
T: Terminated
TTL: TTL Logic
V: Viewing Window

WG Type	Switch Type	RF Freq. (GHz.)	Actuator / Features	IL (dB)	Iso (dB)	DC Power (V)	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-28	SPDT/ DPDT	26.5 - 40	F, TTL, I, M	0.15	55	12	EAR99	PEWGS6058	$5,390.00	$5,174.40	$4,958.80	$4,743.20	15
				0.15	55	28	EAR99	PEWGS6059	$5,390.00	$5,174.40	$4,958.80	$4,743.20	16
			F, I, M	0.15	55	12	EAR99	PEWGS6056	$5,190.00	$4,982.40	$4,774.80	$4,567.20	17
				0.15	55	28	EAR99	PEWGS6057	$5,190.00	$4,982.40	$4,774.80	$4,567.20	18
	SPDT		B, L, S, I, M	0.15	55	12	EAR99	PEWGS6002	$4,290.00	$4,118.40	$3,946.80	$3,775.20	19
				0.15	55	28	EAR99	PEWGS6000	$4,260.00	$4,089.60	$3,919.20	$3,748.80	20
			B, L, TTL, S, I, M	0.15	55	12	EAR99	PEWGS6003	$4,860.00	$4,665.60	$4,471.20	$4,276.80	21
				0.15	55	28	EAR99	PEWGS6001	$4,420.00	$4,243.20	$4,066.40	$3,889.60	22
WR-34	SPDT/ DPDT	22 - 33	L, S, SI, M, V	0.15	60	12	EAR99	PEWGS6042	$5,190.00	$4,982.40	$4,774.80	$4,567.20	23
				0.15	60	28	EAR99	PEWGS6040	$5,270.00	$5,059.20	$4,848.40	$4,637.60	24
			L, TTL, S, SI, M, V	0.15	60	12	EAR99	PEWGS6043	$5,390.00	$5,174.40	$4,958.80	$4,743.20	25
				0.15	60	28	EAR99	PEWGS6041	$5,390.00	$5,174.40	$4,958.80	$4,743.20	26
WR-42	SPDT	18 - 26.5	B, L, S, I, M	0.15	60	12	EAR99	PEWGS6006	$4,290.00	$4,118.40	$3,946.80	$3,775.20	27
				0.15	60	28	EAR99	PEWGS6004	$4,200.00	$4,032.00	$3,864.00	$3,696.00	28
			B, L, TTL, S, I, M	0.15	60	12	EAR99	PEWGS6007	$4,580.00	$4,396.80	$4,213.60	$4,030.40	29
				0.15	60	28	EAR99	PEWGS6005	$4,420.00	$4,243.20	$4,066.40	$3,889.60	30
WR-62		12.4 - 18	B, L, S, I, M	0.1	60	12	EAR99	PEWGS6010	$4,070.00	$3,907.20	$3,744.40	$3,581.60	31
				0.1	60	28	EAR99	PEWGS6008	$4,200.00	$4,032.00	$3,864.00	$3,696.00	32
			B, L, TTL, S, I, M	0.1	60	12	EAR99	PEWGS6011	$4,570.00	$4,387.20	$4,204.40	$4,021.60	33
				0.1	60	28	EAR99	PEWGS6009	$4,960.00	$4,761.60	$4,563.20	$4,364.80	34
WR-75		10 - 15	B, L, S, I, M	0.05	75	12	EAR99	PEWGS6014	$4,070.00	$3,907.20	$3,744.40	$3,581.60	35
				0.05	75	28	EAR99	PEWGS6012	$4,420.00	$4,243.20	$4,066.40	$3,889.60	36
			B, L, TTL, S, I, M	0.05	75	12	EAR99	PEWGS6015	$4,070.00	$3,907.20	$3,744.40	$3,581.60	37
				0.05	75	28	EAR99	PEWGS6013	$4,750.00	$4,560.00	$4,370.00	$4,180.00	38
WR-90	SPDT/ DPDT	8.2 - 12.4	F, TTL, I, M	0.07	80	12	EAR99	PEWGS6062	$5,190.00	$4,982.40	$4,774.80	$4,567.20	39
				0.07	80		EAR99	PEWGS6066	$5,350.00	$5,136.00	$4,922.00	$4,708.00	40

WAVEGUIDE ELECTROMECHANICAL RELAY SWITCHES





Features:
A: Absorptive
AR: Auto Reset
B: Break Before Make
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
M: Manual Override
N: Normally Open
NT: Non-Terminated
P: Pulse Latching
R: Reflective
RS: Reset
S: Self Cut Off
SI: Set Indincator
T: Terminated
TTL: TTL Logic
V: Viewing Window

WG Type	Switch Type	RF Freq. (GHz.)	Actuator / Features	IL (dB)	Iso (dB)	DC Power (V)	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-90	SPDT/ DPDT	8.2 - 12.4	F, TTL, I, M	0.07	80	28	EAR99	PEWGS6063	$5,190.00	$4,982.40	$4,774.80	$4,567.20	41
				0.07	80		EAR99	PEWGS6067	$5,350.00	$5,136.00	$4,922.00	$4,708.00	42
			F, I, M	0.07	80	12	EAR99	PEWGS6060	$4,990.00	$4,790.40	$4,590.80	$4,391.20	43
				0.07	80		EAR99	PEWGS6064	$5,150.00	$4,944.00	$4,738.00	$4,532.00	44
				0.07	80	28	EAR99	PEWGS6061	$4,990.00	$4,790.40	$4,590.80	$4,391.20	45
				0.07	80		EAR99	PEWGS6065	$5,150.00	$4,944.00	$4,738.00	$4,532.00	46
	SPDT		B, L, S, I, M	0.07	80	12	EAR99	PEWGS6018	$5,130.00	$4,924.80	$4,719.60	$4,514.40	47
				0.07	80	28	EAR99	PEWGS6016	$4,790.00	$4,598.40	$4,406.80	$4,215.20	48
			B, L, TTL, S, I, M	0.07	80	12	EAR99	PEWGS6019	$5,070.00	$4,867.20	$4,664.40	$4,461.60	49
				0.07	80	28	EAR99	PEWGS6017	$4,420.00	$4,243.20	$4,066.40	$3,889.60	50
WR-102	SPDT/ DPDT	7 - 11	L, S, SI, M, V	0.06	80	12	EAR99	PEWGS6038	$5,190.00	$4,982.40	$4,774.80	$4,567.20	51
				0.06	80	28	EAR99	PEWGS6036	$5,190.00	$4,982.40	$4,774.80	$4,567.20	52
			L, TTL, S, SI, M, V	0.06	80	12	EAR99	PEWGS6039	$5,390.00	$5,174.40	$4,958.80	$4,743.20	53
				0.06	80	28	EAR99	PEWGS6037	$5,440.00	$5,222.40	$5,004.80	$4,787.20	54
WR-112	SPDT/ DPDT	7.05 - 10	F, TTL, I, M	0.05	80	12	EAR99	PEWGS6070	$5,550.00	$5,328.00	$5,106.00	$4,884.00	55
				0.05	80	28	EAR99	PEWGS6071	$5,550.00	$5,328.00	$5,106.00	$4,884.00	56
			F, I, M	0.05	80	12	EAR99	PEWGS6068	$5,350.00	$5,136.00	$4,922.00	$4,708.00	57
				0.05	80	28	EAR99	PEWGS6069	$5,350.00	$5,136.00	$4,922.00	$4,708.00	58
	SPDT		B, L, S, I, M	0.05	80	12	EAR99	PEWGS6022	$4,070.00	$3,907.20	$3,744.40	$3,581.60	59
				0.05	80	28	EAR99	PEWGS6020	$4,200.00	$4,032.00	$3,864.00	$3,696.00	60
			B, L, TTL, S, I, M	0.05	80	12	EAR99	PEWGS6023	$4,290.00	$4,118.40	$3,946.80	$3,775.20	61
				0.05	80	28	EAR99	PEWGS6021	$4,200.00	$4,032.00	$3,864.00	$3,696.00	62
WR-137		5.85 - 8.2	B, L, S, I, M	0.02	70	12	EAR99	PEWGS6026	$4,070.00	$3,907.20	$3,744.40	$3,581.60	63
				0.02	70	28	EAR99	PEWGS6024	$4,420.00	$4,243.20	$4,066.40	$3,889.60	64
			B, L, TTL, S, I, M	0.02	70	12	EAR99	PEWGS6027	$4,070.00	$3,907.20	$3,744.40	$3,581.60	65
				0.02	70	28	EAR99	PEWGS6025	$4,200.00	$4,032.00	$3,864.00	$3,696.00	66
WR-159	SPDT/ DPDT	4.9 - 7.05	L, S, SI, M, V	0.06	70	12	EAR99	PEWGS6034	$5,190.00	$4,982.40	$4,774.80	$4,567.20	67
				0.06	70	28	EAR99	PEWGS6032	$5,190.00	$4,982.40	$4,774.80	$4,567.20	68
			L, TTL, S, SI, M, V	0.06	70	12	EAR99	PEWGS6035	$5,390.00	$5,174.40	$4,958.80	$4,743.20	69
				0.06	70	28	EAR99	PEWGS6033	$5,440.00	$5,222.40	$5,004.80	$4,787.20	70
WR-187		3.95 - 5.85	L, S, SI, M, V	0.02	80	12	EAR99	PEWGS6030	$5,190.00	$4,982.40	$4,774.80	$4,567.20	71
				0.02	80	28	EAR99	PEWGS6028	$5,190.00	$4,982.40	$4,774.80	$4,567.20	72
			L, TTL, S, SI, M, V	0.002	80	12	EAR99	PEWGS6031	$5,390.00	$5,174.40	$4,958.80	$4,743.20	73
				0.02	80	28	EAR99	PEWGS6029	$5,390.00	$5,174.40	$4,958.80	$4,743.20	74

DOUBLE RIDGE WAVEGUIDE ELECTROMECHANICAL RELAY SWITCHES





Features:
A: Absorptive
AR: Auto Reset
B: Break Before Make
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
M: Manual Override
N: Normally Open
NT: Non-Terminated
P: Pulse Latching
R: Reflective
RS: Reset
S: Self Cut Off
SI: Set Indincator
T: Terminated
TTL: TTL Logic
V: Viewing Window

WG Type	Switch Type	RF Freq. (GHz.)	Actuator / Features	IL (dB)	Iso (dB)	DC Power (V)	ECCN	Model No	1	2-4	5-9	10+	ROW
WRD-180	SPDT/ DPDT	18 - 40	L, S, SI, M, V	0.4	50	12	EAR99	PEWGS6054	$10,200.00	$9,792.00	$9,384.00	$8,976.00	75
				0.4	50	28	EAR99	PEWGS6052	$10,200.00	$9,792.00	$9,384.00	$8,976.00	76
			L, TTL, S, SI, M, V	0.4	50	12	EAR99	PEWGS6055	$10,400.00	$9,984.00	$9,568.00	$9,152.00	77
				0.4	50	28	EAR99	PEWGS6053	$10,400.00	$9,984.00	$9,568.00	$9,152.00	78
WRD-650		6.5 - 18	L, S, SI, M, V	0.35	60	12	EAR99	PEWGS6046	$9,190.00	$8,822.40	$8,454.80	$8,087.20	79
				0.35	60	28	EAR99	PEWGS6044	$9,330.00	$8,956.80	$8,583.60	$8,210.40	80
			L, TTL, S, SI, M, V	0.35	60	12	EAR99	PEWGS6047	$9,390.00	$9,014.40	$8,638.80	$8,263.20	81
				0.35	60	28	EAR99	PEWGS6045	$9,390.00	$9,014.40	$8,638.80	$8,263.20	82
WRD-750		7.5 - 18	L, S, SI, M, V	0.3	60	12	EAR99	PEWGS6050	$9,190.00	$8,822.40	$8,454.80	$8,087.20	83
				0.3	60	28	EAR99	PEWGS6048	$9,190.00	$8,822.40	$8,454.80	$8,087.20	84
			L, TTL, S, SI, M, V	0.3	60	12	EAR99	PEWGS6051	$9,390.00	$9,014.40	$8,638.80	$8,263.20	85
				0.3	60	28	EAR99	PEWGS6049	$9,390.00	$9,014.40	$8,638.80	$8,263.20	86

ELECTROMECHANICAL RELAY SWITCHES
see page 328

WAVEGUIDE FIXED ATTENUATORS





Waveguide Type	RF Frequency (GHz.)	Flange Type	Atten. (dB)	VSWR	ECCN	Model No	1-24	25-49	50-99	100+	ROW
WR-10	75 - 110	Round Cover UG-387/U-Mod	3	1.15:1	EAR99	PEWAT1012-3	$1,500.00	$1,395.00	$1,290.00	$1,200.00	87
			6		EAR99	PEWAT1012-6	$1,500.00	$1,395.00	$1,290.00	$1,200.00	88
			10		EAR99	PEWAT1012-10	$1,500.00	$1,395.00	$1,290.00	$1,200.00	89
			20		EAR99	PEWAT1012-20	$1,500.00	$1,395.00	$1,290.00	$1,200.00	90
			30		EAR99	PEWAT1012-30	$1,500.00	$1,395.00	$1,290.00	$1,200.00	91
WR-12	60 - 90	Round Cover UG-387/U	3		EAR99	PEWAT1011-3	$1,500.00	$1,395.00	$1,290.00	$1,200.00	92
			6		EAR99	PEWAT1011-6	$1,500.00	$1,395.00	$1,290.00	$1,200.00	93
			10		EAR99	PEWAT1011-10	$1,500.00	$1,395.00	$1,290.00	$1,200.00	94
			20		EAR99	PEWAT1011-20	$1,500.00	$1,395.00	$1,290.00	$1,200.00	95
			30		EAR99	PEWAT1011-30	$1,500.00	$1,395.00	$1,290.00	$1,200.00	96
WR-15	50 - 75	Round Cover UG-385/U	3		EAR99	PEWAT1010-3	$1,500.00	$1,395.00	$1,290.00	$1,200.00	97
			6		EAR99	PEWAT1010-6	$1,500.00	$1,395.00	$1,290.00	$1,200.00	98
			10		EAR99	PEWAT1010-10	$1,500.00	$1,395.00	$1,290.00	$1,200.00	99
			20		EAR99	PEWAT1010-20	$1,500.00	$1,395.00	$1,290.00	$1,200.00	1
			30		EAR99	PEWAT1010-30	$1,500.00	$1,395.00	$1,290.00	$1,200.00	2
WR-19	40 - 60	Round Cover UG-383/U-Mod	3		EAR99	PEWAT1009-3	$1,730.00	$1,608.90	$1,487.80	$1,384.00	3
			6		EAR99	PEWAT1009-6	$1,730.00	$1,608.90	$1,487.80	$1,384.00	4
			10		EAR99	PEWAT1009-10	$1,730.00	$1,608.90	$1,487.80	$1,384.00	5
			20		EAR99	PEWAT1009-20	$1,730.00	$1,608.90	$1,487.80	$1,384.00	6
			30		EAR99	PEWAT1009-30	$1,730.00	$1,608.90	$1,487.80	$1,384.00	7
WR-22	33 - 50	Round Cover UG-383/U	3		EAR99	PEWAT1008-3	$1,730.00	$1,608.90	$1,487.80	$1,384.00	8
			6		EAR99	PEWAT1008-6	$1,730.00	$1,608.90	$1,487.80	$1,384.00	9
			10		EAR99	PEWAT1008-10	$1,730.00	$1,608.90	$1,487.80	$1,384.00	10
			20		EAR99	PEWAT1008-20	$1,730.00	$1,608.90	$1,487.80	$1,384.00	11
			30		EAR99	PEWAT1008-30	$1,730.00	$1,608.90	$1,487.80	$1,384.00	12
WR-28	27 - 40	UG-599/U	3		EAR99	PEWAT1007-3	$1,730.00	$1,608.90	$1,487.80	$1,384.00	13
			6		EAR99	PEWAT1007-6	$1,730.00	$1,608.90	$1,487.80	$1,384.00	14
			10	1.2:1	EAR99	PEWAT1007-10	$1,730.00	$1,608.90	$1,487.80	$1,384.00	15
			20		EAR99	PEWAT1007-20	$1,730.00	$1,608.90	$1,487.80	$1,384.00	16
			30	1.15:1	EAR99	PEWAT1007-30	$1,730.00	$1,608.90	$1,487.80	$1,384.00	17

FLEXIBLE WAVEGUIDES

Seamless





Waveguide Type	RF Frequency (GHz.)	IL (dB)	Max VSWR	Length (in)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-22	33 - 50	0.49	1.2:1	6	Round Cover UG-383/U	EAR99	PE-W22SF005-6	$1,910.00	$1,833.60	$1,757.20	$1,680.80	18
		0.49	1.2:1	12	Round Cover UG-383/U	EAR99	PE-W22SF005-12	$2,860.00	$2,745.60	$2,631.20	$2,516.80	19
		0.49	1.2:1	24	Round Cover UG-383/U	EAR99	PE-W22SF005-24	$3,860.00	$3,705.60	$3,551.20	$3,396.80	20
WR-28	26.5 - 40	0.49	1.2:1	12	Square Cover UG-599/U	EAR99	PE-W28SF005-12	$1,620.00	$1,555.20	$1,490.40	$1,425.60	21
		0.98	1.2:1	24	Square Cover UG-599/U	EAR99	PE-W28SF005-24	$2,570.00	$2,467.20	$2,364.40	$2,261.60	22
		1.47	1.2:1	36	Square Cover UG-599/U	EAR99	PE-W28SF005-36	$3,590.00	$3,446.40	$3,302.80	$3,159.20	23
WR-34	22 - 33	0.4	1.15:1	12	Square Cover UG-1530/U	EAR99	PE-W34SF005-12	$1,560.00	$1,497.60	$1,435.20	$1,372.80	24
		0.8	1.15:1	24	Square Cover UG-1530/U	EAR99	PE-W34SF005-24	$2,440.00	$2,342.40	$2,244.80	$2,147.20	25
		1.2	1.15:1	36	Square Cover UG-1530/U	EAR99	PE-W34SF005-36	$3,590.00	$3,446.40	$3,302.80	$3,159.20	26
WR-42	18 - 26.5	0.27	1.15:1	12	Square Cover UG-595/U	EAR99	PE-W42SF005-12	$1,370.00	$1,315.20	$1,260.40	$1,205.60	27
		0.54	1.15:1	24	Square Cover UG-595/U	EAR99	PE-W42SF005-24	$2,220.00	$2,131.20	$2,042.40	$1,953.60	28
		0.81	1.15:1	36	Square Cover UG-595/U	EAR99	PE-W42SF005-36	$3,080.00	$2,956.80	$2,833.60	$2,710.40	29
WR-51	15 - 22	0.18	1.1:1	12	Square Cover	EAR99	PE-W51SF005-12	$1,310.00	$1,257.60	$1,205.20	$1,152.80	30
		0.36	1.1:1	24	Square Cover	EAR99	PE-W51SF005-24	$2,110.00	$2,025.60	$1,941.20	$1,856.80	31
		0.54	1.1:1	36	Square Cover	EAR99	PE-W51SF005-36	$2,970.00	$2,851.20	$2,732.40	$2,613.60	32
WR-62	12.4 - 18	0.14	1.08:1	12	Square Cover UG-419/U	EAR99	PE-W62SF005-12	$1,310.00	$1,257.60	$1,205.20	$1,152.80	33
		0.28	1.08:1	24	Square Cover UG-419/U	EAR99	PE-W62SF005-24	$1,900.00	$1,824.00	$1,748.00	$1,672.00	34
		0.42	1.08:1	36	Square Cover UG-419/U	EAR99	PE-W62SF005-36	$2,700.00	$2,592.00	$2,484.00	$2,376.00	35
WR-75	10 - 15	0.12	1.07:1	12	Square Cover	EAR99	PE-W75SF005-12	$1,290.00	$1,238.40	$1,186.80	$1,135.20	36
		0.24	1.07:1	24	Square Cover	EAR99	PE-W75SF005-24	$2,070.00	$1,987.20	$1,904.40	$1,821.60	37
		0.36	1.07:1	36	Square Cover	EAR99	PE-W75SF005-36	$2,820.00	$2,707.20	$2,594.40	$2,481.60	38

Seamless





Waveguide Type	RF Frequency (GHz.)	IL (dB)	Max VSWR	Length (in)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-90	8.2 - 12.4	0.09	1.07:1	12	Square Cover UG-39/U	EAR99	PE-W90SF005-12	$1,370.00	$1,315.20	$1,260.40	$1,205.60	39
		0.18	1.07:1	24	CPR-90G	EAR99	PE-W90SF006-24	$1,950.00	$1,872.00	$1,794.00	$1,716.00	40
		0.18	1.07:1		Square Cover UG-39/U	EAR99	PE-W90SF005-24	$2,050.00	$1,968.00	$1,886.00	$1,804.00	41
		0.27	1.07:1	36	CPR-90G	EAR99	PE-W90SF006-36	$2,640.00	$2,534.40	$2,428.80	$2,323.20	42
		0.27	1.07:1		Square Cover UG-39/U	EAR99	PE-W90SF005-36	$2,780.00	$2,668.80	$2,557.60	$2,446.40	43
		0.9	1.07:1	12	CPR-90G	EAR99	PE-W90SF006-12	$1,250.00	$1,200.00	$1,150.00	$1,100.00	44
WR-112	7.05 - 10	0.08	1.07:1		CPR-112G	EAR99	PE-W112SF006-12	$1,350.00	$1,296.00	$1,242.00	$1,188.00	45
		0.08	1.07:1		Square Cover UG-51/U	EAR99	PE-W112SF005-12	$1,370.00	$1,315.20	$1,260.40	$1,205.60	46
		0.16	1.07:1	24	CPR-112G	EAR99	PE-W112SF006-24	$2,120.00	$2,035.20	$1,950.40	$1,865.60	47
		0.16	1.07:1		Square Cover UG-51/U	EAR99	PE-W112SF005-24	$2,150.00	$2,064.00	$1,978.00	$1,892.00	48
		0.24	1.07:1	36	CPR-112G	EAR99	PE-W112SF006-36	$2,900.00	$2,784.00	$2,668.00	$2,552.00	49
		0.24	1.07:1		Square Cover UG-51/U	EAR99	PE-W112SF005-36	$2,900.00	$2,784.00	$2,668.00	$2,552.00	50
WR-137	5.85 - 8.2	0.06	1.07:1	12	CPR-137G	EAR99	PE-W137SF006-12	$1,380.00	$1,324.80	$1,269.60	$1,214.40	51
		0.06	1.07:1		Round Cover UG-344/U	EAR99	PE-W137SF005-12	$1,500.00	$1,440.00	$1,380.00	$1,320.00	52
		0.12	1.07:1	24	CPR-137G	EAR99	PE-W137SF006-24	$2,370.00	$2,275.20	$2,180.40	$2,085.60	53
		0.12	1.07:1		Round Cover UG-344/U	EAR99	PE-W137SF005-24	$2,390.00	$2,294.40	$2,198.80	$2,103.20	54
		0.18	1.07:1	36	CPR-137G	EAR99	PE-W137SF006-36	$3,210.00	$3,081.60	$2,953.20	$2,824.80	55
		0.18	1.07:1		Round Cover UG-344/U	EAR99	PE-W137SF005-36	$3,270.00	$3,139.20	$3,008.40	$2,877.60	56

Twistable




Waveguide Type	RF Frequency (GHz.)	IL (dB)	Max VSWR	Length (in)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-22	33 - 50	0.6	1.3:1	6	Round Cover UG-383/U	EAR99	PE-W22TF005-6	$960.00	See Web for Volume Pricing	57
		0.6	1.3:1	12	Round Cover UG-383/U	EAR99	PE-W22TF005-12	$975.00		58
		0.6	1.3:1	24	Round Cover UG-383/U	EAR99	PE-W22TF005-24	$1,030.00		59
WR-28	26.5 - 40	0.6	1.3:1	12	Square Cover UG-599/U	EAR99	PE-W28TF005-12	$635.00		60
		1.2	1.3:1	24	Square Cover UG-599/U	EAR99	PE-W28TF005-24	$710.00		61
		1.8	1.3:1	36	Square Cover UG-599/U	EAR99	PE-W28TF005-36	$695.00		62
WR-34	22 - 33	0.5	1.22:1	12	Square Cover UG-1530/U	EAR99	PE-W34TF005-12	$590.00		63
		1	1.22:1	24	Square Cover UG-1530/U	EAR99	PE-W34TF005-24	$665.00		64
		1.5	1.22:1	36	Square Cover UG-1530/U	EAR99	PE-W34TF005-36	$710.00		65
WR-42	18 - 26.5	0.35	1.3:1	12	Square Cover UG-595/U	EAR99	PE-W42TF005-12	$545.00		66
		0.7	1.3:1	24	Square Cover UG-595/U	EAR99	PE-W42TF005-24	$580.00		67
		1.05	1.35:1	36	Square Cover UG-595/U	EAR99	PE-W42TF005-36	$605.00		68
WR-51	15 - 22	0.55	1.15:1	12	Square Cover	EAR99	PE-W51TF005-12	$575.00		69
		1.1	1.15:1	24	Square Cover	EAR99	PE-W51TF005-24	$600.00		70
		1.65	1.15:1	36	Square Cover	EAR99	PE-W51TF005-36	$665.00		71
WR-62	12.4 - 18	0.28	1.1:1	12	Square Cover UG-419/U	EAR99	PE-W62TF005-12	$640.00		72
		0.56	1.1:1	24	Square Cover UG-419/U	EAR99	PE-W62TF005-24	$745.00		73
		0.84	1.1:1	36	Square Cover UG-419/U	EAR99	PE-W62TF005-36	$765.00		74
WR-75	10 - 15	0.18	1.1:1	12	Square Cover	EAR99	PE-W75TF005-12	$705.00		75
		0.36	1.1:1	24	Square Cover	EAR99	PE-W75TF005-24	$700.00		76
		0.54	1.1:1	36	Square Cover	EAR99	PE-W75TF005-36	$755.00		77
WR-90	8.2 - 12.4	0.15	1.07:1	12	CPR-90G	EAR99	PE-W90TF006-12	$600.00		78
		0.15	1.1:1		Square Cover UG-39/U	EAR99	PE-W90TF005-12	$760.00		79
		0.3	1.07:1	24	CPR-90G	EAR99	PE-W90TF006-24	$745.00		80
		0.36	1.1:1		Square Cover UG-39/U	EAR99	PE-W90TF005-24	$810.00		81
		0.45	1.07:1	36	CPR-90G	EAR99	PE-W90TF006-36	$795.00		82
		0.45	1.1:1		Square Cover UG-39/U	EAR99	PE-W90TF005-36	$875.00		83
WR-112	7.05 - 10	0.12	1.07:1	12	CPR-112G	EAR99	PE-W112TF006-12	$755.00		84
		0.12	1.3:1		Square Cover UG-51/U	EAR99	PE-W112TF005-12	$780.00		85
		0.24	1.07:1	24	CPR-112G	EAR99	PE-W112TF006-24	$845.00		86
		0.24	1.07:1		Square Cover UG-51/U	EAR99	PE-W112TF005-24	$795.00		87
		0.36	1.07:1	36	CPR-112G	EAR99	PE-W112TF006-36	$885.00		88
		0.36	1.07:1		Square Cover UG-51/U	EAR99	PE-W112TF005-36	$885.00		89

Twistable




Waveguide Type	RF Frequency (GHz.)	IL (dB)	Max VSWR	Length (in)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
WR-137	5.85 - 8.2	0.07	1.05:1	12	CPR-137G	EAR99	PE-W137TF006-12	$725.00		See Web for Volume Pricing		90
		0.07	1.05:1		Round Cover UG-344/U	EAR99	PE-W137TF005-12	$725.00				91
		0.14	1.05:1	24	CPR-137G	EAR99	PE-W137TF006-24	$830.00				92
		0.14	1.05:1		Round Cover UG-344/U	EAR99	PE-W137TF005-24	$910.00				93
		0.18	1.05:1	36	Round Cover UG-344/U	EAR99	PE-W137TF005-36	$1,030.00				94
		0.21	1.05:1		CPR-137G	EAR99	PE-W137TF006-36	$945.00				95

WAVEGUIDE FREQUENCY MULTIPLIERS




WG Type	Input Freq. Range (GHz.)	Output Freq. Range (GHz.)	Typ. Output Power (dBm)	Typ. Harmonics	Max. DC Voltage (V)	Typ. DC Current (mA)	ECCN	Model No	1-24	25-49	50-99	100+	ROW
WR-10	12.5 - 18.33	75 - 11	10	-15	8	270	3A001.B.4.E.3	PE88X2026	$15,900.00	$15,105.00	$14,310.00	$13,674.00	96
WR-12	10 - 15	60 - 90	4	-15		197	EAR99	PE88X2024	$12,900.00	$12,255.00	$11,610.00	$11,094.00	97
			5	-15		231	3A001.B.4.E.2	PE88X2025	$15,000.00	$14,250.00	$13,500.00	$12,900.00	98
WR-15	12.5 - 18.75	50 - 75	5	-15		275	EAR99	PE88X2023	$12,725.00	$12,088.75	$11,452.50	$10,943.50	99
WR-19	10 - 15	40 - 60	0	-15		153	EAR99	PE88X2022	$12,375.00	$11,756.25	$11,137.50	$10,642.50	1
WR-28	13.25 - 20	26.5 - 40	5	-15		350	EAR99	PE88X2021	$10,600.00	$10,070.00	$9,540.00	$9,116.00	2

WAVEGUIDE GUNN OSCILLATORS






WG Type	Center Freq. (GHz.)	Tuning Range (GHz.)	Freq. Stability (MHz/deg C)	Phase Noise (dBc/Hz)	Output Power (dBm)	Flange Type	ECCN	Model No	1-9	10-24	25-49	50+	ROW
WR-28	35	3		-95	13	Square Cover UG-599/U	EAR99	PEWGN1010	$9,140.00	$8,683.00	$8,226.00	$7,860.40	3
		3		-95	13	Square Cover UG-599/U	EAR99	PEWGN1011	$8,830.00	$8,388.50	$7,947.00	$7,593.80	4
WR-42	24.125	1	-0.8	-98	10	Square Cover UG-595/U	EAR99	PEWGN1012	$1,570.00	$1,491.50	$1,413.00	$1,350.20	5
WR-90	9.375	0.25		-105	10	Square Cover UG-39/U	EAR99	PEWGN1013	$4,430.00	$4,208.50	$3,987.00	$3,809.80	6

WAVEGUIDE ISOLATORS






WG Type	RF Freq. (GHz.)	Min Isolation (dB)	Max IL (dB)	Max VSWR	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-10	75 - 110	25	2.3	1.5:1	UG-387/U-Mod	EAR99	PEWIR1000	$3,120.00	$2,995.20	$2,870.40	$2,745.60	7
WR-12	60 - 90		2	1.5:1	UG-387/U	EAR99	PEWIR1001	$3,260.00	$3,129.60	$2,999.20	$2,868.80	8
WR-15	50 - 75		1.8	1.4:1	UG-385/U	EAR99	PEWIR1002	$3,140.00	$3,014.40	$2,888.80	$2,763.20	9
WR-19	40 - 60		1.6	1.4:1	UG-383/U-Mod	EAR99	PEWIR1003	$3,260.00	$3,129.60	$2,999.20	$2,868.80	10
WR-22	33 - 50		1.5	1.4:1	UG-383/U	EAR99	PEWIR1004	$3,210.00	$3,081.60	$2,953.20	$2,824.80	11
WR-28	26.5 - 40				UG-599/U	EAR99	PEWIR1015	$3,450.00	$3,312.00	$3,174.00	$3,036.00	12
WR-42	18 - 26.5				UG-597/U	EAR99	PEWIR1010	$2,880.00	$2,764.80	$2,649.60	$2,534.40	13
WR-62	12.4 - 18				UG-1665/U	EAR99	PEWIR1009	$2,790.00	$2,678.40	$2,566.80	$2,455.20	14
WR-75	10 - 15					EAR99	PEWIR1008	$2,690.00	$2,582.40	$2,474.80	$2,367.20	15

WAVEGUIDE ISOLATORS



WG Type	RF Freq. (GHz.)	Min Isolation (dB)	Max IL (dB)	Max VSWR	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-90	8.2 - 12.4				UG-135/U	EAR99	PEWIR1007	$2,740.00	$2,630.40	$2,520.80	$2,411.20	16
WR-112	7.05 - 10				UG-138/U	EAR99	PEWIR1006	$2,850.00	$2,736.00	$2,622.00	$2,508.00	17

WAVEGUIDE LOW NOISE AMPLIFIERS





WG Type	Gain (dB)	Gain Variation ± (dB)	NF (dB)	P1dB (dBm)	Max. DC Voltage (V)	Typ. DC Current (mA)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-10	30		6	9.5	12	70	UG-387/U-Mod	3A001.B.4.E.3	PEWGA3206	$12,375.00	$11,632.50	$11,013.75	$10,518.75	18
WR-12			4.7	22	12	330	UG-387/U	EAR99	PEWGA3205	$12,200.00	$11,468.00	$10,858.00	$10,370.00	19
WR-15	31		5.5	14	12	90	UG-385/U	EAR99	PEWGA3204	$12,025.00	$11,303.50	$10,702.25	$10,221.25	20
WR-19	36			14.5	12	90	UG-383/U-Mod	EAR99	PEWGA3203	$11,150.00	$10,481.00	$9,923.50	$9,477.50	21
WR-22	32			22	8	650	UG-383/U	EAR99	PEWGA3202	$12,200.00	$11,468.00	$10,858.00	$10,370.00	22
WR-28	22	0.75	3	13.5	15	125	UG-599/U	EAR99	PEWGA3208	$3,480.00	$3,271.20	$3,097.20	$2,958.00	23
	33			24	12	280		EAR99	PEWGA3201	$11,500.00	$10,810.00	$10,235.00	$9,775.00	24

WAVEGUIDE MAGIC TEES




Waveguide Type	RF Frequency (GHz.)	Flange Type	IL (dB)	Min Isolation (dB)	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-10	75 - 110	Round Cover UG-387/U-Mod	1	25	EAR99	PEWMT1000	$3,220.00	$3,091.20	$2,962.40	$2,833.60	25
WR-12	60 - 90	Round Cover UG-387/U			EAR99	PEWMT1001	$3,250.00	$3,120.00	$2,990.00	$2,860.00	26
WR-15	50 - 75	Round Cover UG-385/U			EAR99	PEWMT1002	$3,090.00	$2,966.40	$2,842.80	$2,719.20	27
WR-19	40 - 60	Round Cover UG-383/U-Mod	0.8		EAR99	PEWMT1003	$2,790.00	$2,678.40	$2,566.80	$2,455.20	28
WR-22	33 - 50	Round Cover UG-383/U	0.7		EAR99	PEWMT1004	$2,790.00	$2,678.40	$2,566.80	$2,455.20	29
WR-28	26.5 - 40	Square Cover UG-599/U	0.5		EAR99	PEWMT1005	$2,650.00	$2,544.00	$2,438.00	$2,332.00	30
WR-42	18 - 26.5	Square Cover UG-595/U			EAR99	PEWMT1006	$2,600.00	$2,496.00	$2,392.00	$2,288.00	31

WAVEGUIDE ORTHOMODE TRANSDUCERS






RF Freq. (GHz.)	H to A IL (dB)	V to A IL (dB)	H to V Isolation (dB)	H to A Cross Polarization (dB)	V to A Cross Polarization (dB)	Waveguide Type	ECCN	Model No	1	2-4	5-9	10+	ROW
60 - 90	1.2	0.8	40	35	35	WR-12	EAR99	PEWOT0009	$5,600.00	$5,404.00	$5,208.00	$5,040.00	32
30 - 42	0.5	0.5		35	35	WR-28	EAR99	PEWOT0003	$5,890.00	$5,683.85	$5,477.70	$5,301.00	33
26.5 - 40				35	35		EAR99	PEWOT0007	$5,570.00	$5,375.05	$5,180.10	$5,013.00	34
24 - 33	0.6		45	35	35	WR-34	EAR99	PEWOT0001	$6,210.00	$5,992.65	$5,775.30	$5,589.00	35
8.2 - 12.4						WR-90	EAR99	PEWOT0014	$4,460.00	$4,303.90	$4,147.80	$4,014.00	36

WAVEGUIDE PHASE SHIFTERS




WG Type	RF Freq. (GHz.)	Phase Range (GHz.)	Input Power (Watts)	IL (dB)	Length (in)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-10	75 - 110	0 - 180°	0.6	1	3	Round Cover UG-387/U-Mod	EAR99	PE-W10PS1001	$2,560.00	$2,457.60	$2,355.20	$2,252.80	37
WR-12	60 - 90	0 - 180°	0.7	1	3	Round Cover UG-387/U	EAR99	PE-W12PS1001	$2,650.00	$2,544.00	$2,438.00	$2,332.00	38
WR-15	50 - 75	0 - 180°	0.8	1	3	Round Cover UG-385/U	EAR99	PE-W15PS1001	$2,620.00	$2,515.20	$2,410.40	$2,305.60	39
WR-22	33 - 50	0 - 180°	1	1	4	Round Cover UG-383/U	EAR99	PE-W22PS1001	$2,650.00	$2,544.00	$2,438.00	$2,332.00	41
WR-28	26.5 - 40	0 - 180°	1		4	Square Cover UG-599/U	EAR99	PE-W28PS1002	$3,420.00	$3,283.20	$3,146.40	$3,009.60	42
WR-42	18 - 26.5	0 - 180°	1.5	1	4	Square Cover UG-595/U	EAR99	PE-W42PS1001	$2,650.00	$2,544.00	$2,438.00	$2,332.00	43

PIN DIODE SWITCHES, see page 335

WAVEGUIDE POLARIZERS




Band	RF Freq. (GHz.)	Typ Band-width (GHz)	Typ IL (dB)	Typ Axial Ratio (dB)	Length (in)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
Ku	14 - 16	±1	0.5	1.1	3	Square Cover-UG-419/U-Mod	EAR99	PEWPL0000	$4,880.00	$4,709.20	$4,538.40	$4,392.00	48
Ka	26 - 33	±3.5		1.1	2	Square Cover-UG-599/U-Mod	EAR99	PEWPL0005	$4,880.00	$4,709.20	$4,538.40	$4,392.00	49
V	58 - 63	±2.5		1.1	1.31	Round Cover-UG-385/U-Mod	EAR99	PEWPL0008	$4,880.00	$4,709.20	$4,538.40	$4,392.00	50

WAVEGUIDE ROTARY JOINTS




WG Size	Design	Max. Rotation Speed (RPM)	Max.Input Power (Watts)	Max. Input VSWR	Max. Insertion Loss (dB)	Body Material and Plating	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-28	L-Style	30	100	1.2:1	0.35	Brass, Paint	EAR99	PEW28RJ0001	$4,070.00	$3,907.20	$3,744.40	$3,581.60	53
WR-34				1.25:1	0.35	Brass, Paint	EAR99	PEW34RJ0001	$3,430.00	$3,292.80	$3,155.60	$3,018.40	54
WR-62	Inline Style			1.2:1	0.3	Aluminum, Paint	EAR99	PEW62RJ0002	$2,960.00	$2,841.60	$2,723.20	$2,604.80	55
	L-Style			1.2:1	0.3	Aluminum, Paint	EAR99	PEW62RJ0001	$2,980.00	$2,860.80	$2,741.60	$2,622.40	56
WR-75	Inline Style			1.2:1	0.3	Aluminum, Paint	EAR99	PEW75RJ0003	$2,160.00	$2,073.60	$1,987.20	$1,900.80	57
	L-Style			1.2:1	0.3	Brass, Paint	EAR99	PEW75RJ0002	$2,980.00	$2,860.80	$2,741.60	$2,622.40	58
	U-Style			1.2:1	0.3	Brass, Paint	EAR99	PEW75RJ0001	$2,920.00	$2,803.20	$2,686.40	$2,569.60	59

WAVEGUIDE ROTARY JOINTS





WG Size	Design	Max. Rotation Speed (RPM)	Max.Input Power (Watts)	Max. Input VSWR	Max. Insertion Loss (dB)	Body Material and Plating	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-90	Inline Style	30	300	1.2:1	0.3	Aluminum, Paint	EAR99	PEW90RJ0002	$3,310.00	$3,177.60	$3,045.20	$2,912.80	60
	L-Style			1.2:1	0.3	Aluminum, Paint	EAR99	PEW90RJ0003	$3,310.00	$3,177.60	$3,045.20	$2,912.80	61
	U-Style			1.2:1	0.3	Aluminum, Paint	EAR99	PEW90RJ0001	$3,310.00	$3,177.60	$3,045.20	$2,912.80	62
WR-137	L-Style		1,000	1.25:1	0.3	Brass, Paint	EAR99	PEW137RJ0001	$3,890.00	$3,734.40	$3,578.80	$3,423.20	63
WR-187	Inline Style		600	1.2:1	0.25	Aluminum, Paint	EAR99	PEW187RJ0002	$4,670.00	$4,483.20	$4,296.40	$4,109.60	64
	L-Style		1,000	1.15:1	0.25	Brass, Paint	EAR99	PEW187RJ0001	$4,670.00	$4,483.20	$4,296.40	$4,109.60	65

WAVEGUIDE SECTIONS







WG Type	RF Freq. (GHz.)	IL (dB)	VSWR	Length (in)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-5	140 - 220		1.15:1	1	Round Cover UG-387/U-Mod	EAR99	PEW05S000-1	$740.00	See Web for Volume Pricing	66
				3		EAR99	PEW05S000-3	$655.00		67
				6		EAR99	PEW05S000-6	$890.00		68
				9		EAR99	PEW05S000-9	$950.00		69
				12		EAR99	PEW05S000-12	$1,180.00		70
WR-6	110 - 170	0.35		1		EAR99	PEW06S000-1	$570.00		71
				3		EAR99	PEW06S000-3	$620.00		72
		0.55		6		EAR99	PEW06S000-6	$795.00		73
		0.75		9		EAR99	PEW06S000-9	$915.00		74
		1.5		12		EAR99	PEW06S000-12	$1,060.00		75
WR-8	90 - 140	0.3		1		EAR99	PEW08S000-1	$525.00		76
				3		EAR99	PEW08S000-3	$575.00		77
		0.5		6		EAR99	PEW08S000-6	$785.00		78
		0.7		9		EAR99	PEW08S000-9	$915.00		79
		1.2		12		EAR99	PEW08S000-12	$1,140.00		80
WR-10	75 - 110	0.25		3		EAR99	PEW10S010-3	$580.00		81
		0.5		6		EAR99	PEW10S010-6	$585.00		82
WR-12	60 - 90	0.3		3	Round Cover UG-387/U	EAR99	PEW12S010-3	$445.99		83
		0.8		9		EAR99	PEW12S010-9	$585.00		84
		0.64				EAR99	PE-W12S001-9	$585.00		85
		0.82		12		EAR99	PE-W12S001-12	$605.00		86
WR-15	50 - 75	0.95			Round Cover UG-385/U	EAR99	PEW15S010-12	$795.00		87
		0.2		3		EAR99	PE-W15S001-3	$475.99		88
		0.34	1.06:1	6		EAR99	PE-W15S001-6	$520.00		89
		0.49		9		EAR99	PE-W15S001-9	$570.00		90
		0.64		12		EAR99	PE-W15S001-12	$795.00		91
WR-19	40 - 60	0.2		3	Round Cover UG-383/U-Mod	EAR99	PEW19S010-3	$441.99		92
		0.8		12		EAR99	PEW19S010-12	$640.00		93
		0.15		3		EAR99	PE-W19S001-3	$441.99		94
		0.25		6		EAR99	PE-W19S001-6	$505.00		95
		0.34		9		EAR99	PE-W19S001-9	$570.00		96
		0.44		12		EAR99	PE-W19S001-12	$650.00		97
WR-22	33 - 50	0.25	1.1:1	3	Round Cover UG-383/U	EAR99	PEW22S010-3	$487.99		98
		0.13				EAR99	PE-W22S001-3	$437.99		99
		0.21	1.06:1	6		EAR99	PE-W22S001-6	$459.99		1
		0.29		9		EAR99	PE-W22S001-9	$520.00		2
		0.36		12		EAR99	PE-W22S001-12	$630.00		3
			1.09:1	4		EAR99	PEWSP1000	$720.00		4

WAVEGUIDE SECTIONS








WG Type	RF Freq. (GHz.)	IL (dB)	VSWR	Length (in)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-28	26.5 - 40	0.2	1.06:1	3	Square Cover UG-599/U	EAR99	PEW28S010-3	$449.99		5
				6		EAR99	PEW28S010-6	$505.00		6
		0.22		9		EAR99	PE-W28S001-9	$540.00		7
			1.09:1	4		EAR99	PEWSP1001	$640.00		8
WR-34	20 - 33		1.07:1		Square Cover UG-1530/U	EAR99	PEWSP1002	$660.00		9
WR-42	18 - 26.5	0.18	1.06:1	12	Square Cover UG-595/U	EAR99	PE-W42S001-12	$650.00		10
		0.12		6		EAR99	PE-W42S001A-6	$453.99		12
		0.15		9		EAR99	PE-W42S001A-9	$615.00		13
			1.07:1	4		EAR99	PEWSP1003	$640.00		14
WR-51	15 - 22	0.11	1.06:1	9	UBR180	EAR99	PE-W51S001-9	$453.99		15
		0.13		12		EAR99	PE-W51S001-12	$615.00		16
			1.07:1	4	Square Cover	EAR99	PEWSP1004	$680.00		17
WR-62	12.4 - 18		1.03:1	3	Square Cover UG-419/U	EAR99	PE-W62S001-3	$415.99		18
				6		EAR99	PE-W62S001-6	$395.99		19
				9		EAR99	PE-W62S001-9	$403.99		20
				12		EAR99	PE-W62S001-12	$411.99		21
		0.08		6		EAR99	PE-W62S002-6	$560.00		23
		0.11		12		EAR99	PE-W62S002-12	$700.00		25
			1.07:1	4		EAR99	PEWSP1005	$655.00		26
WR-75	10 - 15		1.03:1	0	UBR120	EAR99	PE-W75S001-6	$387.99		27
				3		EAR99	PE-W75S001-3	$397.99		29
				9		EAR99	PE-W75S001-9	$395.99		30
			1.07:1	4	Square Cover	EAR99	PEWSP1006	$670.00		31
WR-90	8.2 - 12.4		1.03:1	0	Square Cover UG-39/U	EAR99	PE-W90S001-12	$309.99		32
				3		EAR99	PE-W90S001-3	$289.99		33
					CPR-90G	EAR99	PE-W90S002-3	$367.99		34
				6	Square Cover UG-39/U	EAR99	PE-W90S001-6	$257.99		35
					CPR-90G	EAR99	PE-W90S002-6	$369.99		36
				9		EAR99	PE-W90S002-9	$369.99		37
				12	CPR-90G	EAR99	PE-W90S002-12	$383.99		39
			1.07:1	4	Square Cover UG-39/U	EAR99	PEWSP1007	$690.00		40
					CPR-90G	EAR99	PEWSP1008	$690.00		41
WR-112	7.05 - 10		1.03:1	3	Square Cover UG-51/U	EAR99	PE-W112S001-3	$391.99		42
				6		EAR99	PE-W112S001-6	$375.99		43
				9		EAR99	PE-W112S001-9	$431.99		44
				12		EAR99	PE-W112S001-12	$397.99		45
			1.07:1	4		EAR99	PEWSP1009	$700.00		46
					CPR-112G	EAR99	PEWSP1010	$705.00		47
WR-137	5.85 - 8.2		1.03:1	0	CPR-137G	EAR99	PE-W137S002-3	$417.99		48
				3	Round Cover UG-344/U	EAR99	PE-W137S001-3	$417.99		50
				6		EAR99	PE-W137S001-6	$421.99		51
				9		EAR99	PE-W137S001-9	$459.99		52
					CPR-137G	EAR99	PE-W137S002-9	$433.99		53
				12	Round Cover UG-344/U	EAR99	PE-W137S001-12	$475.99		54
					CPR-137G	EAR99	PE-W137S002-12	$495.99		55
			1.07:1	4	Round Cover UG-344/U	EAR99	PEWSP1011	$730.00		56
					CPR-137G	EAR99	PEWSP1012	$665.00		57
WRD-180	18 - 40	0.4	1.25:1	0	Square Cover UG	EAR99	PEWRD180S001-3	$685.00		58
		0.5				EAR99	PEWRD180S001-6	$1,150.00		59
WRD-650	6.5 - 18	0.3	1.15:1			EAR99	PEWRD650S001-3	$610.00		60
		0.4				EAR99	PEWRD650S001-6	$1,040.00		61
WRD-750	7.5 - 18	0.3				EAR99	PEWRD750S001-3	$610.00		62
		0.4				EAR99	PEWRD750S001-6	$1,040.00		63

WAVEGUIDE TERMINATIONS




Waveguide Type	RF Frequency (GHz.)	Input Power (Watts)	Max VSWR	Length (in)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-10	75 - 110	0.4	1.06:1		Round Cover UG-387/U	EAR99	PEW10TR0001	$660.00		64
		0.4	1.25:1		Round Cover UG-387/U-Mod	EAR99	PE-W10TR1001	$695.00		65
WR-12	60 - 90	0.6	1.2:1		Round Cover UG-387/U	EAR99	PE-W12TR1001	$675.00		66
WR-15	50 - 75	1	1.2:1	2	Round Cover UG-385/U	EAR99	PEW15TR0001	$705.00		67
WR-19	40 - 60	2	1.06:1		Round Cover UG-383/U	EAR99	PEW19TR0001	$595.00		68
		2	1.09:1		Round Cover UG-383/U-Mod	EAR99	PE-W19TR1001	$625.00		69
WR-22	33 - 50	4	1.05:1		Round Cover UG-383/U	EAR99	PE-W22TR1002	$610.00		70
WR-28	26.5 - 40	0.5	1.02:1		Square Cover UG-599/U	EAR99	PEWTR1000	$845.00		71
		0.5	1.05:1	2	Square Cover	EAR99	PE6809	$1,090.00		72
		0.5	1.3:1	1	Square Cover UG-599/U	EAR99	PE6800	$515.00		73
		1	1.03:1	2	Square Cover UG-599/U	EAR99	PE-W28TR1003	$630.00		74
		40	1.07:1	3	Square Cover	EAR99	PE6818	$1,070.00		75
		50	1.25:1	4	Square Cover UG-599/U	EAR99	PE-W28TR1004	$1,050.00		76
		100	1.25:1	5	Square Cover UG-599/U	EAR99	PE-W28TR1005	$1,740.00		77
	29.4 - 31	2	1.15:1	1	Square Cover UG-599/U	EAR99	PE-W28TR1002	$441.99		78
WR-34	19.6 - 21.2	1	1.15:1		Square Cover UG-597/U	EAR99	PE-W34TR1001	$487.99		79
	22 - 33	0.5	1.05:1	3	Square Cover	EAR99	PE6810	$1,050.00		80
		0.5	1.25:1	1	Square Cover	EAR99	PE6801	$453.99		81
		1	1.25:1		Square Cover UG-1530/U	EAR99	PEWTR1001	$795.00		82
		45	1.1:1		Square Cover	EAR99	PE6819	$1,680.00		83
		75	1.1:1	4	Square Cover	EAR99	PE6828	$1,560.00		84
WR-42	18 - 26.5	0.5	1.05:1	3	Square Cover	EAR99	PE6811	$1,240.00		85
		0.5	1.25:1	1	Square Cover UG-597/U	EAR99	PE6802	$555.00		86
		1	1.02:1		Square Cover UG-595/U	EAR99	PEWTR1002	$735.00		87
		6	1.08:1	3	Square Cover UG-595/U	EAR99	PE-W42TR1001	$660.00		88
		50	1.07:1	4	Square Cover	EAR99	PE6820	$1,130.00		89
	19.6 - 21.2	1	1.15:1	1	Square Cover UG-597/U	EAR99	PE-W42TR1002	$441.99		90
WR-51	15 - 18	1	1.2:1		Square Cover	EAR99	PE6803	$510.00		91
	15 - 22	1	1.02:1		Square Cover	EAR99	PEWTR1003	$760.00		92
		1	1.05:1	3	Square Cover	EAR99	PE6812	$1,280.00		93
WR-62	11.9 - 18	2	1.03:1	4	Square Cover	EAR99	PE6201A	$635.00		94
	12.4 - 18	1.5	1.02:1		Square Cover UG-419/U	EAR99	PEWTR1004	$715.00		95
		2	1.2:1	1	Square Cover	EAR99	PE6804	$575.00		96
		60	1.07:1	4	Square Cover	EAR99	PE6836	$1,150.00		97
	14.5 - 17.8	1	1.05:1	1	Square Cover UG-1665/U	EAR99	PE-W62TR1003	$535.00		98
WR-75	10 - 15	2	1.05:1	4	Square Cover	EAR99	PE6814	$1,030.00		99
		2	1.2:1	1	Square Cover	EAR99	PE6805	$860.00		1
		2.5	1.02:1		Square Cover	EAR99	PEWTR1005	$770.00		2
		75	1.07:1	5	Square Cover	EAR99	PE6823	$1,140.00		3
		175	1.1:1	6	Square Cover	EAR99	PE6832	$1,740.00		4
WR-90	8.2 - 12.4	2	1.05:1	4	Square Cover	EAR99	PE6815	$1,040.00		5
		2	1.2:1	1	Square Cover UG-135/U	EAR99	PE6806	$560.00		6
		4	1.02:1		Square Cover UG-39/U	EAR99	PEWTR1006	$860.00		7
		4	1.02:1		CPR-90G	EAR99	PEWTR1007	$720.00		8
		90	1.07:1	6	Square Cover	EAR99	PE6824	$1,470.00		9
		200	1.1:1		Square Cover	EAR99	PE6833	$1,960.00		10
	8.2 - 12.5	50	1.25:1	4	Square Cover UG-135/U	EAR99	PE-W90TR1002	$1,300.00		11
	9 - 10	2	1.05:1	1	Square Cover UG-135/U	EAR99	PE-W90TR1001	$580.00		12
WR-102	7 - 11	300	1.1:1	7	Square Cover	EAR99	PE6834	$1,980.00		13
WR-112	7.05 - 10	5	1.02:1		CPR-112G	EAR99	PEWTR1009	$815.00		14
		5	1.02:1		Square Cover UG-51/U	EAR99	PEWTR1008	$755.00		15
		300	1.1:1	7	Square Cover UG-51/U	EAR99	PE6835	$2,670.00		16
WR-137	5.38 - 8.17	500	1.25:1	14	CPR-137F	EAR99	PE-W137TR1001	$3,070.00		17
	5.85 - 8.2	6	1.02:1		Round Cover UG-344/U	EAR99	PEWTR1010	$795.00		18
		6	1.02:1		CPR-137G	EAR99	PEWTR1011A	$785.00		19
WR-159	4.64 - 7.05	5	1.03:1	8	CPR-159F	EAR99	PE-W159TR1002	$790.00		20
	4.8 - 5.2	50	1.2:1	4	CPR-159F	EAR99	PE-W159TR1001	$1,470.00		21
WR-187	3.94 - 5.99	5	1.03:1	9	CPR-187F	EAR99	PE-W187TR1002	$700.00		22

See Web for Volume Pricing

See Web for Volume Pricing

See Our Website For Current Pricing & Real-Time Stock Availability!

Waveguides

WAVEGUIDE TERMINATIONS





Waveguide Type	RF Frequency (GHz.)	Input Power (Watts)	Max VSWR	Length (in)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-187	4.4 - 5	70	1.1:1	3	CPR-187F	EAR99	PE-W187TR1001	$835.00	See Web for Volume Pricing	23
WR-229	3.22 - 4.9	5	1.03:1	10	CPR-229F	EAR99	PE-W229TR1001	$930.00		24
		5	1.2:1	3	CPR-229F	EAR99	PE-W229TR1002	$1,030.00		25
WR-284	2.6 - 3.95	5	1.03:1	12	CPR-284F	EAR99	PE-W284TR1001	$1,300.00		26
WRD-180	18 - 40	0.5	1.15:1		Square Cover UG	EAR99	PEWRD180TR1000	$1,670.00		27
WRD-650	6.5 - 18	1	1.15:1		Square Cover UG	EAR99	PEWRD650TR1000	$1,270.00		28
WRD-750	7.5 - 18	1	1.15:1		Square Cover UG	EAR99	PEWRD750TR1000	$1,270.00		29

WAVEGUIDE TRANSITIONS






WG 1 Type	Flange 1 Type	WG 2 Type	Flange 2 Type	VSWR	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-10	Round Cover UG-387/U-Mod	WR-12	Round Cover UG-387/U	1.6:1	EAR99	PE-W10TS12001A	$1,620.00	See Web for Volume Pricing	30
		WR-15	Round Cover UG-385/U	1.45:1	EAR99	PE-W10TS15001	$1,560.00		31
WR-12	Round Cover UG-387/U	WR-15	Round Cover UG-385/U	1.2:1	EAR99	PE-W12TS15001	$1,620.00		33
WR-15	Round Cover UG-385/U	WR-19	Round Cover UG-383/U-Mod	1.1:1	EAR99	PE-W15TS19001	$1,620.00		34
		WR-22	Round Cover UG-383/U	1.15:1	EAR99	PE-W15TS22001	$1,610.00		35
WR-19	Round Cover UG-383/U-Mod	WR-22		1.5:1	EAR99	PE-W19TS22001	$1,560.00		36
		WR-28	Square Cover UG-599/U	1.35:1	EAR99	PE-W19TS28001	$1,620.00		37
WR-22	Round Cover UG-383/U	WR-28		1.35:1	EAR99	PE-W22TS28001	$1,620.00		38
WR-28	Round Cover UG-599/U	WR-51	UBR-180/U-Mod	1.38:1	EAR99	PE-W28TS51001	$1,700.00		40
WR-34	Square Cover UG-1530/U	WR-28	Square Cover UG-599/U	1.08:1	EAR99	PEWTS1010	$995.00		41
WR-42	Square Cover UG-599/U	WR-28	Square Cover UG-595/U	1.1:1	EAR99	PE-W28TS42001A	$1,330.00		42
	Square Cover UG-595/U	WR-34	Square Cover UG-1530/U	1.08:1	EAR99	PEWTS1009	$965.00		43
WR-62	Square Cover UG-1665/U	WR-51	Square Cover	1.08:1	EAR99	PEWTS1007A	$990.00		44
WR-75	Square Cover	WR-62	Square Cover UG-1665/U	1.08:1	EAR99	PEWTS1006	$1,040.00		45
WR-90	Square Cover UG-39/U	WR-75	Square Cover	1.08:1	EAR99	PEWTS1004	$1,170.00		46
	CPR-90G	WR-75		1.08:1	EAR99	PEWTS1005A	$1,050.00		47
WR-112	Square Cover UG-51/U	WR-90	Square Cover UG-39/U	1.08:1	EAR99	PEWTS1002	$1,120.00		48
	CPR-112G	WR-90	CPR-90G	1.08:1	EAR99	PEWTS1003	$1,060.00		49
WR-137	Round Cover UG-344/U	WR-112	Square Cover UG-51/U	1.08:1	EAR99	PEWTS1000	$1,200.00		50
	CPR-137G	WR-112	CPR-112G	1.08:1	EAR99	PEWTS1001	$1,200.00		51

WAVEGUIDE TWISTS





WG Type	RF Freq. (GHz.)	Max VSWR	WG Offset Angle (Deg)	Length (in)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-5	140 - 220		45 Left-hand	1	Square Cover UG-387/U-Mod	EAR99	PEW5TW0001	$670.00	See Web for Volume Pricing	52
			45 Right-hand		Square Cover UG-387/U-Mod	EAR99	PEW5TW0000	$680.00		53
			90 Right-hand		Round Cover UG-387/U-Mod	EAR99	PEW5TW0002	$670.00		54
WR-6	110 - 170		45 Left-hand		Square Cover UG-387/U-Mod	EAR99	PEW6TW0001	$635.00		55
			45 Right-hand		Square Cover UG-387/U-Mod	EAR99	PEW6TW0000	$645.00		56
			90 Right-hand		Round Cover UG-387/U-Mod	EAR99	PEW6TW0002	$645.00		57
WR-8	90 - 140		45 Left-hand		Square Cover UG-387/U-Mod	EAR99	PEW8TW0001	$635.00		58
			45 Right-hand		Square Cover UG-387/U-Mod	EAR99	PEW8TW0000	$645.00		59
			90 Right-hand		Round Cover UG-387/U-Mod	EAR99	PEW8TW0002	$635.00		60

WAVEGUIDE TWISTS






WG Type	RF Freq. (GHz.)	Max VSWR	WG Offset Angle (Deg)	Length (in)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-10	75 - 110	1.1:1	45 Left-hand	1	Round Cover UG-387/U-Mod	EAR99	PE-W10TW1002	$540.00	See Web for Volume Pricing	61
			45 Right-hand		Round Cover UG-387/U-Mod	EAR99	PE-W10TW1003	$530.00		62
		1.43:1	90		Round Cover UG-387/U-Mod	EAR99	PE-W10TW1001	$510.00		63
WR-12	60 - 90	1.12:1	90		Round Cover UG-387/U	EAR99	PE-W12TW1001	$605.00		64
		1.16:1	45 Left-hand		Round Cover UG-387/U	EAR99	PE-W12TW1002	$540.00		65
			45 Right-hand		Round Cover UG-387/U	EAR99	PE-W12TW1003	$540.00		66
			90 Right-hand		Round Cover UG-387/U-Mod	EAR99	PEW12TW001	$605.00		67
WR-15	50 - 75	1.11:1	45 Left-hand	2	Round Cover UG-385/U	EAR99	PE-W15TW1002	$530.00		68
			45 Right-hand		Round Cover UG-385/U	EAR99	PE-W15TW1003	$540.00		69
			90	0	Round Cover UG-385/U	EAR99	PE-W15TW1001A	$510.00		70
WR-22			90		Round Cover UG-383/U	EAR99	PE-W22TW1001	$473.99		76
		1.15:1	90		Round Cover UG-383/U	EAR99	PEW22TW001	$467.99		77
WR-28	26.5 - 40	1.07:1	90	0	Square Cover UG-599/U	EAR99	PE-W28TW1001A	$473.99		78
		1.09:1	45 Left-hand	2	Square Cover UG-599/U	EAR99	PE-W28TW1002	$575.00		79
			45 Right-hand		Square Cover UG-599/U	EAR99	PE-W28TW1003	$575.00		80
		1.1:1	45 Right-hand		Square Cover UG-595/U	EAR99	PEW28TW001	$570.00		81
WR-42	18 - 26.5	1.07:1	90	0	Square Cover UG-595/U	EAR99	PE-W42TW1001A	$493.99		82
		1.25:1	45 Left-hand	3	Square Cover UG-595/U	EAR99	PE-W42TW1002	$560.00		83
			45 Right-hand		Square Cover UG-595/U	EAR99	PE-W42TW1003	$560.00		84
WRD-180	18 - 40	1.35:1	90	0	Square Cover UG	EAR99	PEWRD180TW1001	$1,190.00		85
WRD-650	6.5 - 18		90		Square Cover UG	EAR99	PEWRD650TW1001	$1,080.00		86
WRD-750	7.5 - 18	1.25:1	90		Square Cover UG	EAR99	PEWRD750TW1001	$1,080.00		87

WAVEGUIDES VARIABLE ATTENUATORS



Waveguide Type	RF Frequency (GHz.)	Flange Type	IL (dB)	Max Atten. (dB)	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-10	75 - 110	Round Cover UG-387/U-Mod	1	30	EAR99	PE-W10AT002-30	$2,310.00	$2,217.60	$2,125.20	$2,032.80	88
WR-12	60 - 90	Round Cover UG-387/U	0.4		EAR99	PE-W12AT002-30	$2,380.00	$2,284.80	$2,189.60	$2,094.40	89
WR-15	50 - 75	Round Cover UG-385/U	0.8		EAR99	PE-W15AT001-30	$2,380.00	$2,284.80	$2,189.60	$2,094.40	90
WR-19	40 - 60	Round Cover UG-383/U-Mod	0.6		EAR99	PE-W19AT001-30	$2,330.00	$2,236.80	$2,143.60	Call	91
WR-22	33 - 50	Round Cover UG-383/U	0.5		EAR99	PE-W22AT001-30	$2,280.00	$2,200.20	$2,120.40	$2,052.00	92

WAVEGUIDES VOLTAGE VARIABLE ATTENUATORS





Waveguide Type	RF Frequency (GHz.)	Flange Type	IL (dB)	Atten. Range (dB)	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-10	75 - 110	UG-387/U-Mod	6	0 - 30	EAR99	PEWGA3215	$10,600.00	$10,176.00	$9,752.00	$9,328.00	93
WR-12	60 - 90	UG-387/U	5.5		EAR99	PEWGA3214	$10,600.00	$10,176.00	$9,752.00	$9,328.00	94
WR-15	50 - 75	UG-385/U	5		EAR99	PEWGA3213	$10,250.00	$9,840.00	$9,430.00	$9,020.00	95
WR-19	40 - 60	UG-383/U-Mod	4.5		EAR99	PEWGA3212	$9,540.00	$9,158.40	$8,776.80	$8,395.20	96
WR-22	33 - 50	UG-383/U	4		EAR99	PEWGA3211	$9,190.00	$8,822.40	$8,454.80	$8,087.20	97
WR-28	26.5 - 40	UG-599/U	1.7		EAR99	PEWGA3210	$8,840.00	$8,486.40	$8,132.80	$7,779.20	98

WAVEGUIDE ACCESSORIES

Gasket Kits





Model No	Description	1 Pc. Price	See Web for Volume Pricing			ROW
PEWGK1014	WR-28 Waveguide Electrically Conductive Gasket kit Square Cover, Choke Flange	$129.99				1
PEWGK1000	WR-28 Waveguide Gasket kit Square Cover, Choke Flange, Non-Conductive	$55.99				2
PEWGK1016	WR-51 Waveguide Electrically Conductive Gasket kit Square Cover, Choke Flange	$161.99				3
PEWGK1002	WR-51 Waveguide Gasket kit Square Cover, Choke Flange, Non-Conductive	$53.99				4
PEWGK1017	WR-62 Waveguide Electrically Conductive Gasket kit Square Cover, Choke Flange	$235.99				5
PEWGK1003	WR-62 Waveguide Gasket kit Square Cover, Choke Flange, Non-Conductive	$60.99				6
PEWGK1018	WR-75 Waveguide Electrically Conductive Gasket kit Square Cover, Choke Flange	$149.99				7
PEWGK1004	WR-75 Waveguide Gasket kit Square Cover, Choke Flange, Non-Conductive	$60.99				8
PEWGK1019	WR-90 Waveguide Electrically Conductive Gasket kit Square Cover, Choke Flange	$207.99				9
PEWGK1021	WR-90 Waveguide Electrically Conductive Gasket kit, CPR Flat Flange	$151.99				10
PEWGK1020	WR-90 Waveguide Electrically Conductive Gasket kit, CPR Grooved Flange	$173.99				11
PEWGK1005	WR-90 Waveguide Gasket kit Square Cover, Choke Flange, Non-Conductive	$64.99				12
PEWGK1007	WR-90 Waveguide Gasket kit, CPR90 Flat Flange, Non-Conductive	$73.99				13
PEWGK1006	WR-90 Waveguide Gasket kit, CPR90 Grooved Flange, Non-Conductive	$73.99		See Web for Volume Pricing		14
PEWGK1022	WR-112 Waveguide Electrically Conductive Gasket kit Square Cover, Choke Flange	$181.99				15
PEWGK1024	WR-112 Waveguide Electrically Conductive Gasket kit, CPR Flat Flange	$163.99				16
PEWGK1023	WR-112 Waveguide Electrically Conductive Gasket kit, CPR Grooved Flange	$225.99				17
PEWGK1008	WR-112 Waveguide Gasket kit Square Cover, Choke Flange, Non-Conductive	$64.99				18
PEWGK1010	WR-112 Waveguide Gasket kit, CPR112 Flat Flange, Non-Conductive	$75.99				19
PEWGK1009	WR-112 Waveguide Gasket kit, CPR112 Grooved Flange, Non-Conductive	$75.99				20
PEWGK1026	WR-137 Waveguide Electrically Conductive Gasket kit, CPR Grooved Flange	$211.99				21
PEWGK1027		$181.99				22
PEWGK1025	WR-137 Waveguide Electrically Conductive Gasket kit, Round Cover, Choke Flange	$351.99				23
PEWGK1011	WR-137 Waveguide Gasket kit Round Cover, Choke Flange, Non-Conductive	$66.99				24
PEWGK1013	WR-137 Waveguide Gasket kit, CPR137 Flat Flange, Non-Conductive	$69.99				25
PEWGK1012	WR-137 Waveguide Gasket kit, CPR137 Grooved Flange, Non-Conductive	$77.99				26
PEWGK1015	WR-42, WR-34 Waveguide Electrically Conductive Gasket kit Square Cover, Choke Flange	$149.99				27
PEWGK1001	WR-42, WR-34 Waveguide Gasket kit Square Cover, Choke Flange, Non-Conductive	$53.99				28

Shims





Model No	Description	1-9	10-24	25-49	50+	ROW
PEW10FS2	WR-10 Waveguide Shim, UG-Cover Round flange, 2mm Brass	$145.99	$138.69	$131.39	$125.55	29
PEW12FS2	WR-12 Waveguide Shim, UG-Cover Round flange, 2mm Brass	$131.99	$125.39	$118.79	$113.51	30
PEW15FS2	WR-15 Waveguide Shim, UG-Cover Round flange, 2mm Brass	$131.99	$125.39	$118.79	$113.51	31
PEW19FS3	WR-19 Waveguide Shim, UG-Cover Round flange, 3mm Brass	$131.99	$125.39	$118.79	$113.51	32
PEW22FS3	WR-22 Waveguide Shim, UG-Cover Round flange, 3mm Brass	$131.99	$125.39	$118.79	$113.51	33
PEW28FS3	WR-28 Waveguide Shim, UG-Cover Square flange, 3mm Brass	$171.99	$163.39	$154.79	$147.91	34
PEW34FS4	WR-34 Waveguide Shim, UG-Cover Square flange, 4mm Brass	$171.99	$163.39	$154.79	$147.91	35
PEW42FS4	WR-42 Waveguide Shim, UG-Cover Square flange, 4mm Brass	$167.99	$159.59	$151.19	$144.47	36

Shims



Model No	Description	1-9	10-24	25-49	50+	ROW
PEW75FS5	WR-75 Waveguide Shim, UG-Cover Square flange, 5mm Brass	$91.99	$87.39	$82.79	$79.11	38
PEW90FS5	WR-90 Waveguide Shim, UG-Cover Square flange, 5mm Brass	$91.99	$87.39	$82.79	$79.11	39
PEW112FS5	WR-112 Waveguide Shim, UG-Cover Square flange, 5mm Brass	$109.99	$104.49	$98.99	$94.59	40
PEW137FS7	WR-137 Waveguide Shim, CPR-137F flange, 7mm Brass	$135.99	$129.19	$122.39	$116.95	41
PEW159FS7	WR-159 Waveguide Shim, CPR-159F flange, 7mm Aluminum	$109.99	$104.49	$98.99	$94.59	42
PEW187FS7	WR-187 Waveguide Shim, CPR-187F flange, 7mm Aluminum	$109.99	$104.49	$98.99	$94.59	43
PEW284FS8	WR-284 Waveguide Shim, CPR-284F flange, 8mm Aluminum	$131.99	$125.39	$118.79	$113.51	44
PEW340FS10	WR-340 Waveguide Shim, CPR-340F flange, 10mm Aluminum	$155.99	$148.19	$140.39	$134.15	45
PEW430FS10	WR-430 Waveguide Shim, CPR-430F flange, 10mm Aluminum	$155.99	$148.19	$140.39	$134.15	46

Shorts





Model No	Description	1-9	10-24	25-49	50+	ROW
PEW10SP4	WR-10 Waveguide Short Plate, UG-Cover Round Flange, 4mm Copper	$131.99	$125.39	$118.79	$113.51	47
PEW12SP4	WR-12 Waveguide Short Plate, UG-Cover Round Flange, 4mm Copper	$145.99	$138.69	$131.39	$125.55	48
PEW15SP4	WR-15 Waveguide Short Plate, UG-Cover Round Flange, 4mm Copper	$131.99	$125.39	$118.79	$113.51	49
PEW19SP4	WR-19 Waveguide Short Plate, UG-Cover Round Flange, 4mm Copper	$131.99	$125.39	$118.79	$113.51	50
PEW22SP4	WR-22 Waveguide Short Plate, UG-Cover Round Flange, 4mm Copper	$131.99	$125.39	$118.79	$113.51	51
PEW28SP4	WR-28 Waveguide Short Plate, UG-Cover Square Flange, 5mm Copper	$171.99	$163.39	$154.79	$147.91	52
PEW34SP4	WR-34 Waveguide Short Plate, UG-Cover Square Flange, 4mm Copper	$171.99	$163.39	$154.79	$147.91	53
PEW42SP4	WR-42 Waveguide Short Plate, UG-Cover Square Flange, 4mm Copper	$197.99	$188.09	$178.19	$170.27	54
PEW62SP5	WR-62 Waveguide Short Plate, UG-Cover Square Flange, 5mm Copper	$109.99	$104.49	$98.99	$94.59	55
PEW75SP5	WR-75 Waveguide Short Plate, UG-Cover Square Flange, 5mm Copper	$109.99	$104.49	$98.99	$94.59	56
PEW90SP5	WR-90 Waveguide Short Plate, UG-Cover Square Flange, 5mm Brass	$127.99	$121.59	$115.19	$110.07	57
PEW112SP5	WR-112 Waveguide Short Plate, UG-Cover Square Flange, 5mm Copper	$109.99	$104.49	$98.99	$94.59	58
PEW137SP7	WR-137 Waveguide Short Plate, CPR-137F Flange, 7mm Copper	$131.99	$125.39	$118.79	$113.51	59
PEW159SP7	WR-159 Waveguide Short Plate, CPR-159F Flange, 7mm Aluminum	$109.99	$104.49	$98.99	$94.59	60
PEW187SP7	WR-187 Waveguide Short Plate, CPR-187F Flange, 7mm Aluminum	$109.99	$104.49	$98.99	$94.59	61
PEW284SP8	WR-284 Waveguide Short Plate, CPR-284F Flange, 8mm Aluminum	$131.99	$125.39	$118.79	$113.51	62
PEW340SP10	WR-340 Waveguide Short Plate, CPR-340F Flange, 10mm Aluminum	$223.99	$212.79	$201.59	$192.63	63
PEW430SP10	WR-430 Waveguide Short Plate, CPR-430F Flange, 10mm Aluminum	$223.99	$212.79	$201.59	$192.63	64

Pressure Windows







Model No	Description	1-4	5-9	10-24	25+	ROW
PEWGP1014	WR-28 Waveguide Pressure Window, UG-599/U and UG-599/U-Grooved Flanges, Brass	$830.00	$788.50	$747.00	$713.80	65
PEWGP1013	WR-34 Waveguide Pressure Window, UG Cover and UG Grooved Flanges, Brass	$830.00	$788.50	$747.00	$713.80	66

Pressure Windows



Model No	Description	1-4	5-9	10-24	25+	ROW
PEWGP1012	WR-42 Waveguide Pressure Window, UG-595/U and UG-595/U-Grooved Flanges, Brass	$830.00	$788.50	$747.00	$713.80	67
PEWGP1011	WR-51 Waveguide Pressure Window, UG Cover and UG Grooved Flanges, Brass	$725.00	$688.75	$652.50	$623.50	68
PEWGP1010	WR-62 Waveguide Pressure Window, UG-419/U and UG-419/U-Grooved Flanges, Brass	$725.00	$688.75	$652.50	$623.50	69
PEWGP1009	WR-75 Waveguide Pressure Window, UG Cover and UG Grooved Flanges, Brass	$745.00	$707.75	$670.50	$640.70	70
PEWGP1008	WR-90 Waveguide Pressure Window, UG-39/U and UG-39/U-Grooved Flanges, Brass	$790.00	$750.50	$711.00	$679.40	71
PEWGP1006	WR-112 Waveguide Pressure Window, CPR112F and CPR112G Flanges, Brass	$875.00	$831.25	$787.50	$752.50	72
PEWGP1007	WR-112 Waveguide Pressure Window, UG-51/U and UG-51/U-Grooved Flanges, Brass	$875.00	$831.25	$787.50	$752.50	73
PEWGP1005	WR-137 Waveguide Pressure Window, CPR137F and CPR137G Flanges, Brass	$875.00	$831.25	$787.50	$752.50	74
PEWGP1004	WR-159 Waveguide Pressure Window, CPR159F and CPR159G Flanges, Aluminum	$875.00	$831.25	$787.50	$752.50	75
PEWGP1003	WR-187 Waveguide Pressure Window, CPR187F and CPR187G Flanges, Aluminum	$875.00	$831.25	$787.50	$752.50	76
PEWGP1002	WR-229 Waveguide Pressure Window, CPR229F and CPR229G Flanges, Aluminum	$935.00	$888.25	$841.50	$804.10	77
PEWGP1001	WR-284 Waveguide Pressure Window, CPR284F and CPR284G Flanges, Aluminum	$1,100.00	$1,045.00	$990.00	$946.00	78
PEWGP1000	WR-340 Waveguide Pressure Window, CPR340F and CPR340G Flanges, Aluminum	$1,190.00	$1,130.50	$1,071.00	$1,023.40	79

Miscellaneous






Model No	Description	1 Pc. Price	See Web for Volume Pricing			ROW
PEWAM0000	0.75 inch Diameter Flange, Standard Antenna Mounting Fixture with UG-385/U and UG-387/U Flanges	$630.00				80
PEWAM0001	0.75 inch Square Flange, Standard Antenna Mounting Fixture with UG-599/U Flanges	$630.00				81
PEWAM0002	0.88 inch Square Flange, Standard Antenna Mounting Fixture with UG-595/U and UG-1530/U Flanges	$630.00		See Web for Volume Pricing		82
PEWAM0003	1.125 inch Diameter Flange, Standard Antenna Mounting Fixture with UG-383/U Flanges	$640.00				83
PEWGHW9000	4-40 with 3/32 inch Hex, Stainless Steel Waveguide Flange Screw	$5.79				84
PEWGHW1001	Waveguide Table Jack, Large	$417.99				85
PEWGHW1000	Waveguide Table Jack, Medium	$361.99				86

INDEX GUIDE TO APPENDIX

APPENDIX.....390

PASTERNACK REACH PROGRAM.....391

PASTERNACK RoHS PROGRAM.....391

MAILING LIST CHANGES.....392

BINDING TERMS.....392

PE PART # INDEX.....395

CONVERSION TABLES.....407

MOUNTING HOLES.....409

CONNECTOR IDENTIFIER.....410

CONNECTOR FREQUENCY RANGE CHART.....414

PASTERNACK ENTERPRISES -- REACH PRODUCT COMPLIANCE PROGRAM

OUR COMMITMENT

At Infinite Electronics, we maintain a comprehensive REACH compliance program to help customers with their green aspirations. We strive to have accurate and available material content data on all of our products. When data is not yet available, customer requests will be given top priority.

WHAT IS REACH?

Regulation (EC) No. 1907/2006 of the European Parliament and of the Council of 18 December 2006 is commonly referred to as REACH (Registration, Evaluation, Authorization, and Restriction of Chemicals). The REACH regulation became effective on June 1, 2007 with the objective to improve protection of human health and the environment from exposure to chemicals. Under REACH, there is an obligation to ensure that articles do not contain any of the substances on the REACH Substances of Very High Concern (SVHCs) Candidate list in concentrations greater than 0.1% by weight. SVHCs are substances that may cause cancer or other serious health or environmental effects and thus face potential restriction or outright bans. The SVHC list is updated with additional substances at approximately every six months, thus product declarations must indicate the applicable SVHC release date.

OUR APPROACH

Infinite Electronics has partnered with Assent Compliance, a world class provider of compliance software and professional support staff, to obtain current material content data on our vast selection of electronic products. Together, we work with our supply chain to routinely collect and analyze this data which enables us to determine the state of compliance for each item we sell. As part of our process integration efforts, we are currently redesigning the way this data can be found on-line so that it is consistent across all brands. Once deployed, we will have a customer self-serve search engine tool to enable real-time creation of part number specific declarations. Until then, customers may request declarations directly from our Assent Compliance partners at InfiniteElectronicsRequests@assentcompliance.com. Please ensure you that you list all Infinite Electronics part numbers within your request.

PASTERNACK ENTERPRISES ROHS COMPLIANCE PROGRAM

Lead-free solder is now available for all cable assemblies upon request or online at www.Pasternack.com.

OUR COMMITMENT

At Infinite Electronics, we maintain a comprehensive RoHS compliance program to help customers with their green aspirations. We strive to have accurate and available material content data on all of our products. When data is not yet available, customer requests will be given top priority.

WHAT IS ROHS?

Short for Directive on the restriction of the use of certain hazardous substances in electrical and electronic equipment, RoHS was adopted in February 2003 by the European Union. Now in its third iteration as (EU) Directive 2015/863, RoHS guidelines and legislation are intended to reduce the presence of ten (10) materials deemed hazardous to the environment. To comply, products entering the EU must not have a homogeneous presence of these materials above the following levels by percentage of their weight:

- Lead (Pb) < 0.1%
- Mercury (Hg) < 0.1%
- Cadmium (Cd) < 0.01%
- DEHP < 0.1%
- DBP < 0.1%
- Hexavalent Chromium (CrVI) < 0.1%
- Polybrominated Biphenyls (PBB) < 0.1%
- Polybrominated Diphenyl Esters (PBDE) < 0.1%
- BBP < 0.1%
- DIBP < 0.1%

OUR APPROACH

Infinite Electronics has partnered with Assent Compliance, a world class provider of compliance software and professional support staff, to obtain current material content data on our vast selection of electronic products. Together, we work with our supply chain to routinely collect and analyze this data which enables us to determine the state of compliance for each item we sell. As part of our process integration efforts, we are currently redesigning the way this data can be found on-line so that it is consistent across all brands. Once deployed, we will have a customer self-serve search engine tool to enable real-time creation of part number specific declarations. Until then, customers may request declarations directly from our Assent Compliance partners at InfiniteElectronicsRequests@assentcompliance.com. Please ensure you that you list all Infinite Electronics part numbers within your request.

MAILING LIST CHANGES

If you receive more than one RF Product Guide with the same name and address, please notify Pasternack and pass the RF Product Guide along to a friend. Also, if you do not require multiple copies to the same company address, contact a sales representative to verify and modify your mailing information. A forms-based communications method to add, delete or modify mailing information is available at www.pasternack.com. By clicking "Contact Us", and then clicking "Remove Name from Mailing List", you may complete the form to request a change to your mailing preferences. In addition, by clicking "RF Product Guide", and then clicking "Request a Printed RF Product Guide", you may add your contact information to our mailing list. Please note service opt-in and opt-out options located on the forms. Alternatively, you may mail, email, telephone or fax Pasternack your request.

PLACING YOUR ORDER

► **BY TELEPHONE: 866-PASTERNACK (866-727-8376)**
US & CANADA, OR 949-261-1920

Our friendly sales representatives are ready to serve you from 5:00am to 5:30pm Pacific Standard Time (PST), Monday through Friday. For the most efficient service, please have ready a list of quantities and part numbers and, if paying by credit card, your MasterCard, VISA, American Express or Discover card. Note: Calls may be recorded or monitored for quality and training purposes.

► **BY FAX: 949-261-7451**

Our fax lines can be accessed 7 days a week, 24 hours a day. Orders received after 4:00pm PST will be promptly processed and shipped the next business day. Please include your daytime phone number and/or email address in case we have any questions about your order.

► **BY INTERNET: WWW.PASTERNACK.COM**
OR EMAIL: SALES@PASTERNACK.COM

Order online 7 days a week, 24 hours a day using our online ordering system. Just search for the items you want and add them to your shopping cart. Internet orders entered after 4:00 pm PST will be promptly processed and shipped the next business day.

► **BY MAIL: SIMPLY MAIL YOUR ORDER TO:**
PASTERNACK ENTERPRISES.
17802 FITCH
PO BOX 16759
IRVINE, CA 92623-6759 USA

International customers, please see "International Orders" below for additional information.

TERMS AND CONDITIONS OF SALE:

The following from Pasternack's Binding Terms and Conditions of Sale are provided for your convenience. A complete documentation of the Binding Terms and Conditions of Sale may be found in the back of the RF Product Guide, or on Pasternack's website at https://www.pasternack.com/t-terms-of-sale.aspx. Any questions or clarifications may be answered by contacting Customer Service at (+1) 949-261-1920 or by any of the methods listed above.

NO MINIMUM ORDER REQUIREMENT

GROUND FREIGHT:

Shipping or freight charges and insurance will be paid by the customer. All sales are made FCA-Shipping Point (as defined by the INCOTERMS 2000) in Irvine, CA USA & Lewisville, TX USA. Shipping or freight charges from Pasternack's Irvine, CA factory are prepaid and added to the invoice or billed collect.

SAME-DAY SHIPMENT:

Same-day shipment will apply to orders received Monday through Friday, prior to 4:00pm PST.
- All UPS air and surface options
- All FedEx air options (with an approved account number)
- Most other shipping options, including DHL (with an approved account number) and USPS

COUNTER-TO-COUNTER SHIPPING:

For your urgent order requiring our fastest shipping method, we will place your order on the next available flight from Santa Ana-Orange County John Wayne International Airport (Airport code: SNA) and Dallas/Fort Worth International Airport (Airport Code: DFW) to the destination you specify. Please call for details.

PAYMENT TERMS:

Pasternack offers a number of convenient payment methods:

For United States customers, we offer check, money order, MasterCard, VISA, American Express, and Discover. as well as open account credit to qualified institutions and businesses. Payment must be made in US Dollars.

For Canadian customers, we offer all of the above payment options.
For International customers, see International Orders.

OPEN ACCOUNT CREDIT:

Net 30 Days terms are available to businesses, schools and agencies subject to credit approval. Approval can begin by submitting a completed Credit Application, which can be found online at: www.Pasternack.com/t-CreditApplication.aspx

EFT/WIRE TRANSFERS:

Please contact us for details. We will inform you of the total amount which will include shipping charges and any applicable wire transfer fees. Orders will not be accepted until funds have been received in full.

WELLS FARGO BANK
420 MONTGOMERY ST.
SAN FRANCISCO, CA 94104 USA
ACCOUNT NUMBER: 4270 0000 0000 0000 1
ROUTING NUMBER: 121000248
SWIFT NUMBER: WFBIUS6S

INTERNATIONAL ORDERS:

In addition to the United States and its territories, Pasternack accepts international orders. All orders of international origin are exported from the US in accordance with the Export Administration Regulations. Diversion contrary to US Law is prohibited. Please see Pasternack's Binding Terms and Conditions of Sale for full details.

Pasternack has international distributors for the following countries:
Africa: Namibia, South Africa
Asia-Pacific: Australia, China PRC, India, Indonesia, Japan, Malaysia, New Zealand, Singapore, South Korea, Thailand
Europe: Austria, Belgium, Czech Republic, Denmark, Finland, France, Germany, Ireland, Italy, Kazakhstan, Luxembourg, Netherlands, Norway, Poland, Portugal, Russia, Slovakia, Spain, Sweden, Switzerland, Turkey, United Kingdom
Middle East: Israel
South America: Brazil

To access their complete contact information, please see our International Distributors section in this RF Product Guide. (inside back cover)

INTERNATIONAL SHIPPING CHARGES:

Shipping or freight charges and insurance will be paid by the customer. All sales are made FCA-Shipping Point (as defined by the INCOTERMS 2000) in Irvine, CA USA. We ship orders by UPS, FedEX (with an approved account number), or DHL (with approved account number) with delivery in 2 to 3 days to most locations worldwide.

INTERNATIONAL TAXES AND DUTIES:

Customer is responsible for duties and taxes.

BINDING TERMS AND CONDITIONS OF SALE

1. SCOPE; CHANGES

The terms and conditions stated herein (this "Agreement") govern all sales of products or services ("products") by Infinite Electronics, Inc. (collectively, "we," "us," "our," or "seller") to you or the entity you represent ("you" or "buyer"). You represent to us that you are lawfully able to enter into contracts (e.g., you are not a minor) and that if you are entering into this Agreement for an entity, such as the company you work for, you represent to us that you have the legal authority to bind that entity. Unless otherwise agreed to in writing by seller's authorized agent, any terms and conditions contained in buyer's purchase order or any other document that are different from or in addition to these terms and conditions are objected to, are rejected, and will not be binding on us. By placing an order for products from us, or by accepting delivery of the products described on the applicable packing slip, bill of lading and/or invoice received with the products, you agree to be bound by and accept these terms and conditions of sale.

We may change the terms and conditions of this Agreement in our sole discretion by posting an updated version of these terms and conditions at this location; provided, however, that the terms and condition of this Agreement in effect as of the date of an applicable order shall continue to govern such order and the products purchased thereunder.

2. ORDER ACCEPTANCE

a) Your receipt of an email or other form of order confirmation does not constitute our acceptance of your order or a confirmation of an offer to sell.

b) We reserve the right, without prior notification, to limit the order quantity on any item and/or refuse service to anyone.

c) All orders are subject to review and acceptance by us. You agree to provide complete and accurate contact information in connection with any order submitted to us. Verification of information may be required prior to the acceptance of any order.

d) In the case of pre-stocked finished goods, order acceptance is designated by fulfilling the order. In the case of products requiring post-order processing (including but not limited to design, material purchase, manufacturing or test), order acceptance is designated by performing activities unique to the order.

3. ORDER CANCELLATION

a) Orders fully or partially processed by seller may not be cancelled by buyer.

b) Products not previously stocked as finished goods are both Non-Cancelable and Non-Refundable ("NC/NR"). NC/NR products include cable assemblies, special orders, custom orders, orders for non-standard products, products not customarily in stock, scheduled orders requiring special procurements, or orders for products requiring assembly or manufacturing activities prior to shipping (not stored in completed state) as well as purchased services such as special testing or product modifications.

c) In the event of cancellation or other withdrawal of an order for any reason and without limiting any other remedy as a result of such cancellation or other withdrawal, reasonable cancellation or restocking charges, which shall include all expenses then incurred and commitments made by seller, shall be paid by buyer. Buyer's requests to reschedule are subject to acceptance by seller in its sole discretion. Orders may not be rescheduled after the order has been submitted by seller to the shipment carrier.

4. PRICES

a) Orders are billed at the prices (in US dollars) in effect at the time of shipment.

b) Prices will be as specified within seller's website or as stated in seller's quote / proposal. If no period is specified, quoted prices will be applicable for thirty (30) days.

c) For catalog products, the website contains the most current catalog pricing and is the price reference for such orders. Pricing included in the catalog is for reference only and final pricing is determined by the published website price.

d) For non-catalog products and services, prices cited are based on current costs and are subject to reasonable adjustment on or after the date of acceptance of any purchase order to meet a rise or fall in such costs, as computed on the date of delivery.

e) Prices are subject to change without notice.

f) Prices are exclusive of taxes, impositions and other charges, including: sales, use, excise, value added and similar taxes or charges imposed by any government authority, international shipping charges, forwarding agent's and broker's fees, bank fees, consular fees, document fees and import duties.

5. TERMS OF PAYMENT

a) All payments must be in US Dollars, or will be converted to US Dollars using seller's standard exchange rate at the time of purchase.

b) MasterCard, VISA, Discover, and American Express credit cards, purchase cards and major bank debit cards are accepted. Payment via net thirty (30) days is available to businesses, schools and agencies or as otherwise specified by seller subject to credit approval.

c) For International Orders, MasterCard, VISA, and American Express credit cards are accepted. Payment via open credit account with Net thirty (30) days may be established for companies having three U.S. references accepted to seller. Prepaid Wire Transfer: You can wire the funds to our bank. We will contact you with the total amount, which will include shipping charges and a $40 wire transfer fee. Orders will not be accepted until funds have been received in full and the Purchase Order (PO) has been received. Notwithstanding anything to the contrary in this Agreement, seller may add or remove payment options in seller's sole discretion.

d) Buyer acknowledges that seller has the right to reassess buyer's creditworthiness from time to time. To the extent such is in accordance with law, in the event there is a decline in buyer's creditworthiness, seller may, upon thirty (30) days written notice, revise the payment terms between the parties. Upon request, buyer shall provide financial data evidencing the buyer's worth in order for seller to determine the creditworthiness of buyer. Such information shall include, but not be limited to, annual reports, balance sheets, and bank records.

e) If buyer is delinquent in its payment obligations, without prejudice to any other remedies available to it by law or in equity, seller may demand immediate payment and at seller's option (i) suspend all further deliveries to be made under the purchase order or any further performance under any other contract with buyer or buyer's affiliates, in which event buyer shall not be released in any respect from its obligations to seller under the purchase order; (ii) recover all costs of collection including but not limited to reasonable attorneys' fees; (iii) repossess the product for which payment has not been made; (vi) charge interest at 1.5% per month on the past due amount, not to exceed the interest percentage allowed by law; and (vii) reassess the credit worthiness of buyer and change any current payment terms. Any discount from seller's rates, if any, shall cease to apply to the delinquent invoice, buyer shall be invoiced for such differences in cost, and shall immediately pay the resulting invoice.

6. TAXES AND DUTIES

a) Any taxes related to the products purchased are the responsibility of buyer (excluding taxes based on seller's net income), unless buyer presents an exemption certificate acceptable to seller and the applicable taxing authorities. If any exemption certificate presented by buyer is held to be invalid, then buyer will pay seller the amount of the tax and any penalties and interest related thereto.

b) If possible, seller will bill taxes as a separate item on the invoice presented to buyer.

c) Sales tax will be charged on product cost and shipping & handling where applicable and required by law. Any sales tax due that is not collected by the seller is the responsibility of the buyer.

d) International orders may be subject to various taxes and duties in the country of destination, all of which are the responsibility of the buyer. This includes sales, use, excise, value added and similar taxes or charges imposed by any government authority, international shipping charges, forwarding agent's and broker's fees, bank fees, consular fees, document fees and import duties.

7. SHIPPING COSTS

Shipping or freight charges and insurance will be paid by the buyer and added to the invoice or billed collect unless specifically stated in the quote or order confirmation based on seller practices or promotions.

8. DELIVERY AND TITLE

a) Unless otherwise agreed to in writing, all products are shipped Incoterms 2010 - FCA Shipping Point. Subject to seller's right of stoppage in transit, delivery of the products to the carrier will constitute delivery to buyer and title and risk of loss will pass to buyer.

b) Seller will make reasonable efforts to initiate shipment and schedule delivery as close as possible to buyer's requested delivery date(s). Buyer acknowledges that delivery dates provided by seller are estimates only and that seller will not be liable for failure to deliver on such dates.

c) Selection of the carrier and delivery route will be made by seller unless specifically designated by buyer.

d) Seller reserves the right to make deliveries in installments. Delay in delivery of one installment will not entitle buyer to cancel any other installment(s). Delivery of any installment of products within thirty (30) days after the date requested will constitute a timely delivery. Delivery of a quantity that varies from the quantity specified shall not relieve buyer of the obligation to accept delivery and pay for the products delivered.

e) Deliveries shall be made during normal business hours Monday through Friday. One attempt to deliver will be made. Should delivery need to be rescheduled, any additional costs incurred for redelivery and/or storage fees will be charged to the buyer. Seller shall use reasonable efforts to make timely delivery but shall be excused from any delays arising out of causes beyond its reasonable control. Any specific delivery dates that may be stated are approximate.

f) If completion of delivery is prevented through no fault of seller, seller may specify a reasonable alternative place of delivery. Buyer agrees that all costs of storage and transport incurred following an initial attempt at delivery are hereby allocated to and imposed upon buyer, and shall be added by seller to the sale price. Delivery may at any time be withheld by seller pending payment of any sum due from the buyer to seller. Seller will return Product via the incoming method unless an alternative method has been indicated on the purchase order or a change authorized by the buyer representative.

g) Deliveries made outside the 48 contiguous States may be subject to modified terms and conditions as stated within the order quote.

9. LIMITED WARRANTY

a) Products manufactured and/or branded by seller are warranted for a period of one year from time of delivery against defects in workmanship or materials or failure to operate as described in product data sheets under normal use. In some cases, the warranty period may exceed one year where a written warranty description specific to a certain product is stated in a contract or posted on a company website, product catalog or user's manual. Accessories and consumable goods such as batteries, chargers and accessory cables are warranted for four months.

b) Products manufactured by seller in accordance with buyer's instructions or specifications provided by seller are warranted for a period of one year from time of delivery against defects in workmanship or materials only under normal use. In some cases, the warranty period may exceed one year where a written warranty description specific to a certain product is stated in a contract or posted on a company website, product catalog or user's manual.

c) Calibration services are warranted for a period of one year from time of completion against defects in workmanship or materials or failure to operate as described in product data sheets under normal use.

d) The warranties set forth in this Section 9 shall not apply to any defect, failure, or damage arising from or in connection with: (i) improper use, or improper or inadequate maintenance and care; (ii) modifications to or repairs of the products performed by any party other than seller; (iii) combination of the products with any other technology, equipment, hardware, software, or other materials; (iv) use of the products in an environment not meeting the operating specifications for the products; (v) failure to properly transport, prepare, and store the products; (vi) acts of God; or (vii) any normal wear and tear or normal environmental degradation.

e) Products solely distributed by seller without alteration carry the warranty of the respective manufacturer only.

f) Seller will at seller's option and in seller's sole discretion, repair, replace or refund any products that are returned under warranty, and Seller's repair, replacement, or refunding of the price paid for a product under warranty shall be seller's sole liability, and buyer's sole remedy, for any breach of the warranties in this Section 9.

g) This warranty applies to the original purchaser only and is not transferable.

h) This warranty does not cover damage incurred during shipment which is the responsibility of the freight shipping company.

i) Buyer will bear the costs of access, de-installation, re-installation and transportation of the products to seller and back to buyer in connection with any warranty claims. Seller will reimburse the costs of transportation to seller and bear the costs of returning the repaired product or sending replacement product to buyer if the product is found to be covered under warranty.

j) Any repair or replacement pursuant to this limited warranty for products manufactured and/or branded by seller shall be warranted against the same defects re-occurring in a period of 12 months from time of delivery of the repaired or replaced product, or until the expiration of the original product warranty, which ever shall be the latter.

k) This limited warranty and remedies are expressly conditioned upon: (i) buyer's payment of the purchase price in full, (ii) buyer giving written notice of the defect, reasonably described, to seller within ten (10) days of the time when buyer discovers or ought to have discovered the defect, (iii) the storage, installation, operation, use, and maintenance of the products in compliance with product instructions, (iv) the existence of proper records of buyer's operation and maintenance of the products during the warranty period, (v) buyer providing seller with a reasonable opportunity to examine the products and the aforementioned records, and (vi) the absence of any unauthorized modification or repair of the products, including without limitation the removal or alternation of any serial numbers or product identifications.

l) THIS WARRANTY IS IN LIEU OF ANY AND ALL OTHER WARRANTIES, WHETHER ORAL, WRITTEN, EXPRESSED, IMPLIED OR STATUTORY. ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE AND NON-INFRINGEMENT ARE HEREBY DISCLAIMED.

10. RETURNS

a) Buyers wishing to return products must first obtain a Return Material Authorization (RMA) number from a Customer Service representative. Unauthorized returns will not be accepted at point of receipt. The RMA number must be printed on the outside of the package in order for it to be received and processed. Merchandise must be shipped prepaid.

b) Seller will determine in seller's sole discretion the appropriate remedies for returned items based on the product's limited warranty and circumstances of the return including a possible refund of purchase price, credit for future purchase, replacement, repair, return to buyer as-is, scrap with consent, and refund of shipping expenses.

c) Items stocked as finished goods and ordered in error must have a Return Material Authorization (RMA) number issued within 30 days of the original order. These parts are eligible for full credit only if the returned products and packaging are in mint and salable condition. A repackaging/restocking charge not to exceed 25% of the sale price may be charged on any products not returned unopened. Under no circumstances will credit be issued after 30 days from date of invoice or for orders exceeding $500.00 in total value. All freight charges are the responsibility of buyer.

d) Products not previously stocked as finished goods are not returnable unless found to be defective. These include cable assemblies, special orders, custom orders, orders for non-standard products, products requiring assembly or manufacturing activities prior to shipping (not stored in completed state).

e) Defective items must have a Return Material Authorization (RMA) number marked on the package prior to shipping.

f) After 30 days from invoice all merchandise returns for distributed products not manufactured by seller must be handled directly with that manufacturer in accordance with their warranty.

11. ORDER DISCREPANCIES

Claims for shortages, incorrect materials or invoicing errors must be made by buyer in writing within ten (10) business days after receipt of shipment. Claims for nonreceipt of shipment must be made in writing within ten (10) business days after receipt of invoice. No products shall be returned without seller's express instructions. Buyer must provide in writing the order number and describe all defects associated with the order.

12. LIMITATION OF LIABILITIES; INDEMNITY

a) IN NO EVENT WILL SELLER BE LIABLE TO BUYER OR TO ANY THIRD PARTY FOR ANY DELAY, FAILURE TO GIVE NOTICE OF DELAY, LOSS OF USE, SECURITY OR DATA BREACH, LOSS OF REVENUE OR PROFIT OR LOSS OF DATA, RECALL COSTS, SERVICE INTERRUPTIONS, DOWNTIME, TESTING, INSTALLATION, REPLACEMENT, OR REMOVAL COSTS, OR FOR ANY CONSEQUENTIAL, INCIDENTAL, INDIRECT, EXEMPLARY, SPECIAL OR PUNITIVE DAMAGES, WHETHER ARISING OUT OF BREACH OF CONTRACT, TORT (INCLUDING NEGLIGENCE), OR OTHERWISE, REGARDLESS OF WHETHER SUCH DAMAGE WAS FORESEEABLE AND WHETHER OR NOT SELLER HAS BEEN ADVISED OF

THE POSSIBILITY OF SUCH DAMAGES. SELLER'S AGGREGATE LIABILITY FOR ANY CLAIMS ARISING OUT OF OR IN CONNECTION WITH THIS AGREEMENT SHALL NOT EXCEED THE PURCHASE PRICE PAID BY BUYER FOR THE PRODUCTS WHICH ARE THE SUBJECT OF THE CLAIM. THE DISCLAIMERS AND LIMITATIONS IN THIS SECTION 12 WILL APPLY NOTWITHSTANDING ANY FAILURE OF ESSENTIAL PURPOSE OF ANY LIMITED REMEDY AND TO THE MAXIMUM EXTENT PERMITTED UNDER APPLICABLE LAW.

b) Buyer shall defend seller from and against any claims, actions, proceedings, or suits brought by any third party (i) alleging infringement of intellectual property rights arising out of or in connection with seller's compliance with buyer's drawings, specifications, requirements or instructions or (ii) arising out of or in connection with the products supplied by seller and incorporated into the buyer's products (each a "Claim") and shall indemnify and hold harmless seller from any costs, liabilities, damages, fines, judgments, or expenses (including reasonable attorneys' fees) arising out of or in connection with any Claim.

13. EXPORT COMPLIANCE

a) Items are controlled by the U.S. Government and authorized for export only to the country of ultimate destination for use by the ultimate consignee or end-user(s) identified in the invoice. They may not be resold, transferred, or otherwise disposed of, to any other country or to any person other than the authorized ultimate consignee or end-user(s), either in their original form or after being incorporated into other items, without first obtaining approval from the U.S. Government or as otherwise authorized by U.S. law and regulations. Buyer agrees to comply with all applicable export control laws, restrictions and regulations of the United States and those of the buyer's country, and shall not export, or transfer for the purpose of re-export, any product to any embargoed country or region, including but not limited to Cuba, the Crimean Region of Ukraine, Iran, North Korea, Sudan, and Syria, or to any denied, blocked, or designated person or entity as mentioned in any such United States or EU law or regulation. Buyer represents and warrants that it is not on the Denied Persons, Specially Designated Nationals or Debarred Persons List, as identified by the U.S. Treasury Office of Foreign Asset Control (OFAC) and by the U.S. Department of Commerce, Bureau of Industry and Security (BIS), or any other United States list of prohibited persons; is not owned or controlled by any person that is on one of those lists, or is otherwise prohibited by United States or other law from purchasing the products or services hereunder, and shall notify the seller immediately if buyer's status related to the above changes. Buyer shall be solely responsible to obtain any license to export, re-export or import as may be required. Buyer also agrees that it will not use these products in connection with the proliferation of weapons of mass destruction, including missiles, nuclear, chemical or biological weapons.

b) Seller shall not be liable for delays or refusals by governmental authorities or other authorities to grant licenses or approvals, nor for suspension or revocation thereof, nor for changes in export classification. Buyer must deliver requested information, including requested end-user information, necessary for export licenses to be granted, and or necessary for seller to determine if a license or other type of authorization is required.

c) For all custom orders, buyer shall provide seller with export classification information for all buyer property and information (including buyer drawings) delivered to seller in relation to this order. Export classification information includes the applicable export control classification, the country of origin and, for hardware only, the Harmonized Tariff Code. For such custom orders, seller will supply buyer with similar export classification information for products and/or information for which seller has design authority. Buyer and seller will promptly notify the other upon a change in classification information if any occurs prior to delivery.

14. GOVERNING LAW; VENUE

a) All matters arising out of or relating to this agreement, or a breach thereof, are governed by and construed in accordance with the internal laws of the State of California without giving effect to any choice or conflict of law provision or rule (whether of the State of California or any other jurisdiction) that would cause the application of the laws of any jurisdiction other than those of the State of California.

b) Any legal suit, action or proceeding arising out of or relating to this agreement, or a breach thereof, will be instituted in the federal or State courts located in the city of Irvine, California or its closest California venue. Each party irrevocably submits to the exclusive jurisdiction of the courts in any legal suit, action or proceeding.

15. LEGAL NOTICES

Any legal notice sent to seller from buyer, required or permitted hereunder, will be deemed to have been effectively delivered if in writing and served by personal delivery or sent by registered or certified mail with return receipt requested, postage prepaid, to seller at the primary address specified as seller's place of business.

16. INTELLECTUAL PROPERTY

a) Notwithstanding delivery of and the passing of title in any product, nothing in these terms and conditions shall have the effect of granting or transferring to, or vesting in, buyer any intellectual property rights in or to any products.

b) The drawings, text, product depictions, logos, content, product descriptions, and organization and taxonomy of seller's website, catalogue, product guides or other documents and media owned by the seller and of the described content there within are proprietary to the seller and protected by intellectual property laws, including but not limited to United States Copyright law and United States Trademark law. Whether seller owns copyrights in these works or not, their content and the selection, arrangement, coordination and structure of the arranged content there within are the sole property of the seller. Use of the above stated materials does not give anyone the right to modify, reproduce, transmit, publish, publicly display, adapt, or create derivative works or in any way exploit any of the materials without express written permission of the seller.

c) All trademarks referenced in seller's catalog or website or depicted within any seller's documents or digital media, whether registered in United States or other countries, may not be used without permission of the respective trademark owner. This applies to seller owned trademarks as well as those of seller's suppliers.

d) SELLER MAKES NO REPRESENTATION OR WARRANTY THAT THE PRODUCTS (OR BUYER'S USE OR EXPLOITATION THEREOF) WILL NOT INFRINGE ANY INTELLECTUAL PROPERTY RIGHTS.

17. SOFTWARE

a) To the extent that the product or services contain or are software, seller hereby grants to buyer a non-exclusive, non-transferable, personal license to use the software and related documentation. Buyer's use conclusively evidences its acceptance of this license. Title to the software shall at all times remain with seller. Buyer agrees that the software, all enhancements, related documentation, and derivative works are, and will remain the sole property of seller and includes valuable trade secrets. Buyer agrees to treat the software and related documentation as confidential and to not copy, reproduce, sub-license, or otherwise disclose the software and related documentation to third parties. Buyer agrees to not disassemble, decompile, reverse engineer, create derivative works from or otherwise translate, customize, localize, modify, add to, or in any way alter, rent, or loan the software or related documentation unless the operation is specifically authorized by law.

b) Third party product software Licenses are separate end user license agreements ("EULA") and not issued pursuant to the above stated personal license.

c) Buyer agrees to defend, indemnify and hold harmless seller from all damages and third party claims arising from unauthorized use or transfer of the software or firmware.

d) If the software is licensed for use in the performance of a U.S. Government prime contract or subcontract, buyer agrees that consistent with FAR 12.211 and 12.212, commercial computer software, computer software documentation and technical data for commercial items are licensed under seller's standard commercial license.

18. CONFIDENTIAL INFORMATION

Buyer agrees that all confidential information furnished by or obtained from seller in connection with the sale of items hereunder (including product data and manufacturing process data) shall be adequately safeguarded to prevent unauthorized disclosure. Buyer agrees not to (i) disclose any such information to any other person or entity, or (ii) use such information for any purpose, other than performing authorized activities directly related to the governing contract.

19. TOLERANCES

Unless otherwise agreed to in writing by seller, standard tolerances as described on seller's drawings, websites and/or posted catalog datasheets shall apply.

20. PRODUCT LINE CHANGES

Product specifications and availability are subject to change without notice. Seller reserves the right to change specifications or discontinue items at seller's sole discretion for any reason whatsoever including, but not limited to changing market conditions, product discontinuation, component unavailability, manufacturing cost changes and errors in advertisements.

21. FCC PART 15 AND PART 97 NOTICE

For systems operating within the jurisdiction of the United States Federal Communications Commission (FCC), buyer acknowledges that any amplification device it purchases is intended for use only in a transmission system certified under Part 15, Part 97 or other applicable section of the rules and regulations of the FCC, or that a legal exception to this requirement applies.

22. ASSIGNMENT

Buyer shall not assign this Agreement or any order hereunder without the prior written consent of the seller. Any assignment in violation of the foregoing will be void and of no force or effect. Seller may assign this Agreement or any order hereunder in seller's sole discretion and without restriction. This Agreement will be binding upon and inure to the benefit of the parties, their successors, and permitted assigns.

23. RELATIONSHIP

Nothing in in this Agreement or any product or service orders shall be construed to place the buyer or seller in the relationship of partners or joint ventures, and the buyer and seller shall have no power to obligate or bind the other in any manner whatsoever.

24. WAIVER

No waiver by seller of any breach of this Agreement by the buyer shall be considered as a waiver of the subsequent breach of the same or any other provision.

25. SEVERABILITY

If any provision or portion of this Agreement shall be adjudged invalid or unenforceable by a court of competent jurisdiction or by operation of any applicable law, that provision or portion of this Agreement shall be deemed omitted and the remaining provisions and portions shall remain in full force and effect.

26. LIENS AND TITLE

a) Buyer hereby grants to seller a security interest in any property owned by the buyer (including buyer's beneficial rights to property leased by seller) in the possession of seller or any of sellers' affiliates, at any time, to secure all amounts owed by buyer to seller under this Agreement.

b) In the case of repairs or overhauls performed pursuant to this Agreement, buyer grants seller a perfected security interest in all products retained in possession of seller upon which any repair or overhaul services have been performed by seller. Buyer further acknowledges and agrees that, in addition to the security interest and lien expressly granted by buyer to seller, seller shall have a lien on the product retained in possession of seller to the extent otherwise provided by law. Buyer acknowledges that the lien (whether granted by buyer or through the operation of law) for repairs or overhaul shall be for the full value of such work, and shall be superior to any lien or interest in favor of buyer, its parents, affiliates, or subsidiaries, or any other person who has knowledge of this Agreement. To the extent that seller maintains possession of product under repair, buyer agrees that seller is a secured creditor of buyer and has all the rights of a secured creditor.

c) With respect to products sold pursuant to this Agreement, buyer agrees and acknowledges that seller shall retain a security interest in such product, unless and until all payment for such products has been made and all other covenants and agreements of this Agreement have been performed in full. Accordingly, buyer agrees that it will not suffer or permit any lien or encumbrance to be established that effects the title to the product sold by seller pursuant hereto until seller has been paid in full. Buyer agrees that, in the event of buyer's insolvency, or in the event that any petition is filed by or against buyer under Chapter 7 or Chapter 11 of the Bankruptcy Code, seller may, at its discretion, recover all products sold pursuant to this Agreement and/or seek damages or costs under applicable laws.

27. STORAGE FEES

A storage fee will be applied monthly up to the maximum allowed by law on all repaired and overhauled units if delivery is not taken within five (5) days of notification.

28. FORCE MAJEURE

Notwithstanding anything else in this Agreement, no default, delay, or failure to perform on the part of seller will be considered a breach of this Agreement if such default, delay, or failure to perform is shown to be due to causes beyond reasonable control of seller, including, but not limited to, causes such as strikes, lockouts or other labor disputes, riots, civil disturbances, actions or inactions of governmental authorities or suppliers, epidemics, war, embargoes, severe weather, fire, earthquakes, acts of God or the public enemy, nuclear disasters, or default of a common carrier.

29. ENTIRE AGREEMENT; CONSTRUCTION; SURVIVAL

This Agreement sets forth the entire agreement and understanding of the Parties relating to the subject matter herein and supersedes all prior and contemporaneous communications, representations, discussions, and agreements between the Parties with respect to such subject matter. The titles and section headings used in this Agreement are for ease of reference only and shall not be used in the interpretation or construction of this Agreement. No rule of construction resolving any ambiguity in favor of the non-drafting party shall be applied hereto. The word "including", when used herein, is illustrative rather than exclusive and means "including, without limitation." In the event of any termination or expiration of this Agreement, buyer's obligations to pay amounts due hereunder and arising prior to the date of termination or expiration, as well as Sections 9, 12–18, and 21–29 shall survive such termination or expiration.

WARNING:

Products in this catalog can expose you to chemicals including phthalates, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information, go to www.P65Warnings.ca.gov. For specific products impacted, please visit www.pasternack.com.

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
CST-400	Web	
DBT-U	Web	
EZ-200-NMH-X	Web	
EZ-200-TFRP	Web	
EZ-200-TF-RP	292	93
EZ-200-TM-X	289	64
EZ-240-4310M-X	246	31
EZ-240-NMH-X	264	34
EZ-240-QM-RA-X	270	39
EZ-240-SM-RA-X	274	87
EZ-240-SM-X	272	12
EZ-240-TM-X	289	65
EZ-400-716M-RA-X	248	94
EZ-400-716M-X	247	74
EZ-400-BM-X	251	1
EZ-400-FM-75	297	24
EZ-400-NF-BH	Web	
EZ-400-NMC-2-D	264	12
EZ-400-NMH-75-X	299	74
EZ-400-NMH-PL-X	264	35
EZ-400-NMH-RA-X	265	83
EZ-400-NMH-X	264	36
EZ-400-TM-X	289	66
EZ-600-716M-X	247	75
EZ-600-NF-BH	267	64
EZ-600-NF-X	266	26
EZ-600-NMC-2-D	264	13
EZ-600-NMH-RA-X	265	84
EZ-600-NMH-X	264	37
EZ-600-TM-X	289	67
FT-396	Web	
LMR-100A-FR	228	18
LMR-100A-PVC	228	19
LMR-100A-UF	228	20
LMR-195	228	21
LMR-195-FR	228	22
LMR-195-LLPL	Web	
LMR-195-UF	228	23
LMR-200	228	24
LMR-200-FR	228	25
LMR-200-UF	228	17
LMR-240	228	26
LMR-240-DB	229	27
LMR-240-FR	229	28
LMR-240-UF	229	29
LMR-400	229	30
LMR-400-75	228	1
LMR-400-DB	229	31
LMR-400-FR	229	32
LMR-400-UF	229	33
LMR-500	229	34
LMR-500-DB	229	35
LMR-500-UF	229	36
LMR-600	229	37
LMR-600-DB	229	38
LMR-600-FR	229	39
LMR-600-UF	229	40
LMR-LW195	229	41
LMR-LW240	229	42
LMR-LW400	229	43
LMR-LW600	229	44
PE-020SR	231	1
PE-034SR	231	2
PE-047SR	231	3
PE-047SR-STRAIGHT	231	4
PE-1/2FAC	229	46
PE-1/2SFHC	229	45
PE-1/4SFHC	229	47
PE-118SR	231	5
PE-B150	228	2
PE-B159-BK	228	3
PE-B159-BL	228	4
PE-B159-GR	228	5
PE-B159-RD	228	6
PE-B159-WH	228	7
PE-B159-YW	228	8
PE-B305	228	9
PE-B400	229	48
PE-C100-LSZH	229	49
PE-C195	229	50
PE-C200	229	51
PE-C240	229	52
PE-C300	229	53
PE-C400	230	54
PE-C500	230	55
PE-C600	230	56
PE-P047	230	57
PE-P086	230	58
PE-P086HF	230	59
PE-P141	230	60
PE-P141HF	230	61
PE-P142LL	230	62
PE-P160LL	230	63
PE-P195	230	64
PE-P300LL	230	65
PE-S330	233	40
PE-SR047AL	232	6
PE-SR047AL-STRAIGHT	232	7
PE-SR047FL	232	8
PE-SR401AL-STRAIGHT	232	9
PE-SR401FL	232	10
PE-SR402-75	232	11
PE-SR402-75-STRAIGHT	232	12
PE-SR402AL	232	13
PE-SR402AL-STRAIGHT	232	14
PE-SR402FL	232	15
PE-SR402FLJ	232	16
PE-SR402TN	232	17
PE-SR402TN-STRAIGHT	232	18
PE-SR405AL	232	19
PE-SR405AL-STRAIGHT	232	20
PE-SR405FL	232	21
PE-SR405FLJ	232	22
PE-SR405TN	232	23
PE-SR405TN-STRAIGHT	232	24
PE-T1000	345	63
PE-T1001	345	64
PE-T1002	346	72
PE-T1003	346	73
PE-T1004	345	62
PE-T1006	Web	
PE-T1008	Web	
PE-T1009	345	61
PE-T1010	346	74
PE-T1011	Web	
PE-T1012	345	71
PE-T1013	Web	
PE-T2000	346	95
PE-T2001	346	91
PE-T2002	Web	
PE-T2003	346	81
PE-T2004	346	98
PE-T2005	Web	
PE-T2006	346	78
PE-T2007	346	86
PE-T2008	Web	
PE-T2009	Web	
PE-T2010	346	5
PE-T2011	346	3
PE-T2012	346	4
PE-T2013	346	11
PE-T2014	346	2
PE-T2015	346	92
PE-T2016	346	88
PE-T2016A	346	9
PE-T2017	346	7
PE-T2018	346	90
PE-T2019	Web	
PE-T2020	Web	
PE-T2021	Web	
PE-T2022	Web	
PE-T2023	346	10
PE-T2024	Web	
PE-T2025	346	6
PE-W10AT002-30	395	88
PE-W10AT5001	384	7
PE-W10B001	376	2
PE-W10B002	376	3
PE-W10CA003	372	87
PE-W10CA004	372	88
PE-W10CP001-10	378	78
PE-W10CP001-20	378	76
PE-W10CP003-10	378	79
PE-W10CP003-20	378	77
PE-W10PS1001	390	37
PE-W10TR1001	393	65
PE-W10TS12001A	394	30
PE-W10TS15001	394	31
PE-W10TS19001	394	32
PE-W10TW1001	395	63
PE-W10TW1002	395	61
PE-W10TW1003	395	62
PE-W112B001	377	27
PE-W112B002	377	28
PE-W112S001-12	392	45
PE-W112S001-3	392	42
PE-W112S001-6	392	43
PE-W112S001-9	392	44
PE-W112SF005-12	387	46
PE-W112SF005-24	387	47
PE-W112SF005-36	387	45
PE-W112SF006-12	387	48
PE-W112SF006-24	387	47
PE-W112SF006-36	387	49
PE-W112TF005-12	387	85
PE-W112TF005-24	387	87
PE-W112TF005-36	387	89
PE-W112TF006-12	387	84
PE-W112TF006-24	387	86
PE-W112TF006-36	387	88
PE-W12AT002-30	395	89
PE-W12AT5001	384	8
PE-W12B001	376	4
PE-W12B002	376	5
PE-W12CA001	372	89
PE-W12CA002	372	90
PE-W12CP001-10	379	83
PE-W12CP001-20	379	81
PE-W12CP003-10	379	84
PE-W12CP003-20	379	82
PE-W12PS1001	390	38
PE-W12S001-12	391	86
PE-W12S001-9	391	85
PE-W12TR1001	393	66
PE-W12TS15001	394	33
PE-W12TW1001	395	64
PE-W12TW1002	395	65
PE-W12TW1003	395	66
PE-W137B001	377	29
PE-W137B002	377	30
PE-W137B003A	377	31
PE-W137B004	377	32
PE-W137S001-12	392	54
PE-W137S001-3	392	50
PE-W137S001-6	392	51
PE-W137S001-9	392	52
PE-W137S002-12	392	55
PE-W137S002-3	392	48
PE-W137S002-9	392	49
PE-W137SF002A-6	392	53
PE-W137SF005-12	387	52
PE-W137SF005-24	387	54
PE-W137SF005-36	387	56
PE-W137SF006-12	387	51
PE-W137SF006-24	387	53
PE-W137SF006-36	387	55
PE-W137TF005-12	388	91
PE-W137TF005-24	388	93
PE-W137TF005-36	388	94
PE-W137TF006-12	388	90
PE-W137TF006-24	388	92
PE-W137TF006-36	388	95
PE-W137TR1001	393	67
PE-W159TR1001	393	21
PE-W159TR1002	393	20
PE-W15AT001-30	395	90
PE-W15AT5001	384	9
PE-W15B001	376	6
PE-W15B002	376	7
PE-W15CA001	372	91
PE-W15CA002	372	92
PE-W15CP001-10	379	87
PE-W15CP001-20	379	86
PE-W15CP003-10	379	88
PE-W15PS1001	390	39
PE-W15S001-12	391	91
PE-W15S001-3	391	88
PE-W15S001-6	391	89
PE-W15S001-9	391	90
PE-W15TS19001	394	34
PE-W15TS22001	394	35
PE-W15TW1001A	395	70
PE-W15TW1002	395	68
PE-W15TW1003	395	69
PE-W187TR1001	394	23
PE-W187TR1002	394	22
PE-W19AT001-30	395	91
PE-W19AT5001	384	10
PE-W19B002	376	8
PE-W19CA001	372	93
PE-W19CA002	372	94
PE-W19CP001-10	379	92
PE-W19CP001-20	379	91
PE-W19CP003-10	379	89
PE-W19CP003-20	379	90
PE-W19PS1001	390	40
PE-W19S001-12	391	95
PE-W19S001-3	391	94
PE-W19S001-6	391	96
PE-W19S001-9	391	93
PE-W19TR1001	393	69
PE-W19TS22001	394	36
PE-W19TW1001	395	71
PE-W19TW1002	395	72
PE-W19TW1003	395	73
PE-W229TR1001	394	24
PE-W229TR1002	394	25
PE-W22AT001-30	395	92
PE-W22AT5001	384	11
PE-W22AT5002	384	12
PE-W22B001	376	11
PE-W22CA001	372	95
PE-W22CA002	372	96
PE-W22CP001-10	379	94
PE-W22CP003-20	379	96
PE-W22PS1001	390	41
PE-W22S001-12	391	3
PE-W22S001-3	391	99
PE-W22S001-6	391	1
PE-W22S001-9	391	2
PE-W22SF005-12	386	18
PE-W22SF005-24	386	20
PE-W22SF005-36	386	19
PE-W22SF006-12	386	17
PE-W22SF006-24	386	21
PE-W22SF006-36	386	18
PE-W22TF005-12	387	58
PE-W22TF005-24	387	59
PE-W22TF005-36	387	57
PE-W22TF006-12	387	70
PE-W22TF006-24	387	69
PE-W22TF006-36	387	71
PE-W22TR1002	393	70
PE-W22TS28001	394	38
PE-W22TS42001	394	39
PE-W22TW1001	395	76
PE-W22TW1002	395	74
PE-W22TW1003	395	75
PE-W284TR1001	394	26
PE-W28AT5001	384	13
PE-W28B002	377	12
PE-W28B003	377	13
PE-W28CA002	373	3
PE-W28CP002-10	379	97
PE-W28CP002-20	379	98
PE-W28CP003-10	379	99
PE-W28F001	376	89
PE-W28F002	376	90
PE-W28PS1002	390	42
PE-W28S001-9	392	7
PE-W28SF005-12	386	21
PE-W28SF005-24	386	22
PE-W28SF005-36	386	23
PE-W28TF005-12	387	60
PE-W28TF005-24	387	61
PE-W28TF005-36	387	62
PE-W28TR1002	393	78
PE-W28TR1003	393	74
PE-W28TR1004	393	76
PE-W28TR1005	393	77
PE-W28TS42001A	394	42
PE-W28TS51001	394	40
PE-W28TW1001A	395	78
PE-W28TW1002	395	79
PE-W28TW1003	395	80
PE-W34SF005-12	386	24
PE-W34SF005-24	386	25
PE-W34SF005-36	386	26
PE-W34TF005-12	387	63
PE-W34TF005-24	387	64
PE-W34TF005-36	387	65
PE-W34TR1001	393	79
PE-W42AT5001	384	14
PE-W42CA001	373	14
PE-W42CA002	373	15
PE-W42CP002-20	379	5
PE-W42CP004-10	379	7
PE-W42CP004-20	379	6
PE-W42F001	376	91
PE-W42F002	376	93
PE-W42F003	376	94
PE-W42F004	376	92
PE-W42PS1001	390	43
PE-W42S001-12	392	10
PE-W42S001A-6	392	12
PE-W42S001A-9	392	13
PE-W42S002-3	392	11
PE-W42SF005-12	386	27
PE-W42SF005-24	386	28
PE-W42SF005-36	386	29
PE-W42TF005-12	387	66
PE-W42TF005-24	387	67
PE-W42TF005-36	387	68
PE-W42TR1001	393	88
PE-W42TR1002	393	90
PE-W42TW1001A	395	82
PE-W42TW1002	395	83
PE-W42TW1003	395	84
PE-W51B001	377	16
PE-W51S001-12	392	16
PE-W51S001-9	392	15
PE-W51SF005-12	386	30
PE-W51SF005-24	386	31
PE-W51SF005-36	386	32
PE-W51TF005-12	387	69
PE-W51TF005-24	387	70
PE-W51TF005-36	387	71
PE-W62B001	377	17
PE-W62B002	377	18
PE-W62B003	377	19
PE-W62B004	377	20
PE-W62S001-12	392	21
PE-W62S001-3	392	18
PE-W62S001-6	392	19
PE-W62S001-9	392	20
PE-W62S002-12	392	25
PE-W62S002-3	392	22
PE-W62S002-6	392	23
PE-W62S002-9	392	24
PE-W62SF005-12	386	33
PE-W62SF005-24	386	34
PE-W62SF005-36	386	35
PE-W62TF005-12	387	72
PE-W62TF005-24	387	73
PE-W62TF005-36	387	74
PE-W62TR1003	393	98
PE-W75B001	377	21
PE-W75B002	377	22
PE-W75S001-3	392	29
PE-W75S001-6	392	27
PE-W75S001-9	392	30
PE-W75S001A-6	392	28
PE-W75SF005-12	386	36
PE-W75SF005-24	386	37
PE-W75SF005-36	386	38
PE-W75TF005-12	387	75
PE-W75TF005-24	387	76
PE-W75TF005-36	387	77
PE-W90B001	377	23
PE-W90B002	377	24
PE-W90B003A	377	25
PE-W90B004A	377	26
PE-W90S001-12	392	32
PE-W90S001-3	392	33
PE-W90S001-6	392	35
PE-W90S001A-9	392	38
PE-W90S002-12	392	39
PE-W90S002-3	392	34
PE-W90S002-6	392	36
PE-W90S002-9	392	37
PE-W90SF005-12	387	39
PE-W90SF005-24	387	41
PE-W90SF005-36	387	43
PE-W90SF006-12	387	44
PE-W90SF006-24	387	40
PE-W90SF006-36	387	42
PE-W90TF005-12	387	79
PE-W90TF005-24	387	81
PE-W90TF005-36	387	83
PE-W90TF006-12	387	78
PE-W90TF006-24	387	80
PE-W90TF006-36	387	82
PE-W90TR1001	393	12
PE-W90TR1002	393	11
PE-W90TW1001	395	76
PE-W90TW1002	395	75
SC-100-TM-D	289	68
SPF-250	232	30
SPF-375	232	31
SPF-500	232	32
SPO-250	233	33
SPO-375	233	34
SPO-500	233	35
SPP-250-LLPL	233	36
SPP-375-LLPL	233	37
SPP-500-LLPL	233	38
ST-396-J	Web	
ST-540-J	Web	
TC-100-SM	Web	
TC-100-TM	Web	
TC-195-NMH-RA-D	265	85
TC-195-NMH-X	264	38
TC-195-SM-SS-X	272	13
TC-195-TM-X	289	69
TC-200-BM-X	251	2
TC-200-NMH-X	264	39
TC-200-SM-SS-X	272	15
TC-240-4310M-X	246	32
TC-240-BMC	251	83
TC-240-BM-X	251	3
TC-240-NF-BH-X	267	68
TC-240-NMC	Web	
TC-240-NMH-X	264	40
TC-240-SM-SS-X	272	16
TC-240-TM-X	289	70
TC-250-4310M-RA-LP	247	52
TC-250-716M-LP	248	86
TC-250-NM-LP	265	65
TC-250-NM-RA-LP	266	4
TC-250-XNM-LP	Web	
TC-375-4310M-LP	247	43
TC-375-716M-LP	248	87
TC-375-NM-LP	265	66
TC-400-4310M-X	246	33
TC-400-BM-X	251	4
TC-400-NF-X	266	27
TC-400-NMH-RA-D	266	95
TC-400-NMH-X	264	41
TC-400-SM-X	272	17
TC-400-TM-RA-D	290	96
TC-400-TM-X	289	71
TC-402-1023M-LP	240	5
TC-402-225M-LP	242	79
TC-402-4195F-LP	246	27
TC-402-4195M-LP	246	21
TC-402-4310F-BH-LP	247	59
TC-402-4310F-LP	247	57
TC-402-4310M-LP	247	46
TC-402-4310M-RA-LP	247	53
TC-402-4310MS-LP	247	47
TC-402-716F-LP	248	22
TC-402-716F-PM-LP	249	32
TC-402-716M-LP	248	89
TC-402-716M-RA-LP	248	2
TC-402-NF-BH-LP	267	82
TC-402-NF-LP	267	46
TC-402-NM-LP	265	67
TC-402-NM-RA-LP	266	5
TC-402-NX10M-LP	269	24
TC-402-NX10M-RA-LP	269	26
TC-402-QM-LP	270	38
TC-402-QM-RA-LP	270	48
TC-402-SM-LP	273	52
TC-402-SM-RA-LP	274	13
TC-500-4310M-LP	247	45
TC-500-716M-LP	248	88
TC-500-NM-LP	265	63
TC-600-4310M-X	246	34
TC-600-NMH-X	264	42
TC-SPO250-NM-RA-LP	Web	
TC-SPO375-4310M-LP	Web	
TC-SPO500-NM-LP	Web	
TC-SPO500-NM-RA-LP	266	2
TC-SPP250-4195M-RALP	246	24
TC-SPP250-4310F-LP	247	56
TC-SPP250-4310M-LP	Web	
TC-SPP250-4310MS-LP	Web	
TC-SPP250-716F-LP	248	19
TC-SPP250-716M-LP	Web	
TC-SPP250-716M-RA-LP	248	1
TC-SPP250-NF-BH-LP	267	81
TC-SPP250-NF-LP	Web	
TC-SPP250-NM-RA-LP	Web	
TC-SPP250-SM-LP	Web	
TC-SPP250-SM-RA-LP	Web	
TC-SPP375-716F-LP	248	21
TC-SPP375-716M-LP	Web	
TC-SPP375-NF-LP	267	44
TC-SPP375-NM-LP	Web	
TC-SPP500-4310M-LP	Web	
TC-SPP500-716M-LP	Web	
TC-SPP500-NM-LP	Web	
TFT-402	231	99
TFT-402-LF	233	39
PE1001-1	Web	
PE1001-2	Web	
PE1001-3	Web	
PE1001-4	Web	
PE1001-5	Web	
PE1001-6	Web	
PE1001-7	Web	
PE1002-1	Web	
PE1002-2	Web	
PE1003-2	Web	
PE1013-2	Web	
PE1013-3	Web	
PE1013-6	Web	
PE1013-7	Web	
PE1004-1-100PK	Web	
PE1004-2-100PK	Web	
PE1004-3-100PK	Web	
PE1005-1-100PK	Web	
PE1005-2-100PK	Web	
PE1005-3-100PK	Web	
PE1006-1-100PK	Web	
PE1006-2-100PK	Web	
PE1007-100PK	Web	
PE1008-100PK	Web	
PE1009-100PK	Web	
PE1010	Web	
PE1015-1	304	68
PE1015-4	304	69
PE1015-5	304	70
PE1015-6	304	71
PE1015-2	304	72
PE1015-3	304	73
PE1015-7	304	75
PE1016-9	304	86
PE1016-8	304	87
PE1016-2	305	88
PE1016-3	305	89
PE1016-5	305	90
PE1016-6	305	91
PE1016-11	305	92
PE1016-12	305	93
PE1016-15	305	94
PE1016-14	305	95
PE1016-1	305	96
PE1016-7	305	97
PE1016-4	305	98
PE1016-10	305	99
PE1016-13	305	1
PE1017-7	304	74
PE1017-2	304	76
PE1017-1	304	77
PE1017-6	304	78
PE1017-5	304	79
PE1017-8	304	80
PE1017-9	304	81
PE1017-10	304	82
PE1017-11	304	83
PE1017-4	304	84
PE1017-3	304	85
PE1276	18	A7
PE1277	18	C6
PE1278	18	D7
PE1279	45	A3
PE1280	25	C6
PE1281	21	D4
PE1400	326	57
PE1401	326	56
PE1402	326	58
PE1406	326	59
PE1513	54	11
PE1514	54	9
PE1516	54	16
PE1517	54	13
PE1518	54	14
PE1519	54	20
PE1520	54	21
PE1521	54	22
PE1522	54	24
PE1523	54	27
PE1524	54	23
PE1525	54	17
PE1528	54	10
PE1603	92	58
PE1604	92	52
PE1605	92	55
PE1606A	92	42
PE1608	92	44
PE1610	92	41
PE1611	92	45
PE1612	92	48
PE1613	92	46
PE1614	92	47
PE1615	92	49
PE1616	92	50
PE1617	92	53
PE1618	92	54
PE1619	92	39
PE1620	92	40
PE1621	92	51
PE1622	92	57
PE11S1001	Web	
PE11S1002	341	11
PE11S3900	341	2
PE11S3901	341	1
PE11S3902	341	12
PE11S3903	341	13
PE11S3904	341	14
PE11S3905	341	15
PE11S3906	341	3
PE11S3907	341	4
PE11S3908	341	5
PE11S3909	341	6
PE11S3910	341	7
PE11S3911	341	8
PE11S3912	341	9
PE11S3913	341	10
PE12D1000	378	69
PE12D1001	378	68
PE12D1002	378	67
PE12D1003	Web	
PE12D1004	378	66
PE12D1005	378	65
PE13U1000	378	75
PE13U1001	378	74
PE13U1002	378	73
PE13U1003	378	72
PE13U1004	378	71
PE13U1005	378	70
PE15A1000	55	72
PE15A1001	56	84
PE15A1002	56	90
PE15A1003	56	99
PE15A1003M	56	98
PE15A1004	56	2
PE15A1005	56	78
PE15A1006	56	89
PE15A1007	55	39
PE15A1008	55	60
PE15A1009	55	56
PE15A1010	56	86
PE15A1011	55	50
PE15A1012	55	52
PE15A1013	55	53
PE15A1014	55	64
PE15A1017	55	68
PE15A1018	55	69
PE15A1019	55	73
PE15A1023	56	76
PE15A1024	56	77
PE15A1025	56	1
PE15A1026	56	97
PE15A1027	56	96
PE15A1028	56	79
PE15A1030	56	87
PE15A1031	56	75
PE15A1032	56	92
PE15A1033	56	95
PE15A1034	56	82
PE15A1035	56	88
PE15A1039	56	80
PE15A1041	56	81
PE15A1042	55	66
PE15A1043	55	45
PE15A1044	55	46
PE15A1045	55	44
PE15A1046	55	40
PE15A1047	55	43
PE15A1048	55	48
PE15A1049	55	51
PE15A1050	55	63
PE15A1051	55	57
PE15A1052	55	54
PE15A1053	55	65
PE15A1054	55	55
PE15A1055	55	41
PE15A1057	55	59
PE15A1059	55	42
PE15A1060	55	62
PE15A1061	55	61
PE15A1062	55	47
PE15A1064	55	58
PE15A1065	55	49
PE15A1066	55	67
PE15A1067	55	71
PE15A1068	55	70
PE15A1070	55	74
PE15A1071	56	94
PE15A1072	56	93
PE15A1073	57	28
PE15A1074	56	22
PE15A1075	56	21
PE15A1076	56	4
PE15A1077	56	5
PE15A2000	Web	
PE15A2001	55	37
PE15A2002	Web	
PE15A2003	55	36
PE15A2004	55	38
PE15A3001	52	23
PE15A3004	52	30
PE15A3005	52	30
PE15A3007	52	18
PE15A3008	52	31
PE15A3009	53	57
PE15A3014	52	26
PE15A3015	52	27
PE15A3016	52	46
PE15A3017	53	73
PE15A3018	53	69
PE15A3019	53	70
PE15A3020	53	75
PE15A3021	52	24
PE15A3022	53	52
PE15A3023	52	17
PE15A3024	53	80
PE15A3025	53	86
PE15A3036	Web	
PE15A3037	54	97
PE15A3038	53	58
PE15A3253	52	33
PE15A3254	52	15
PE15A3255	52	19
PE15A3256	52	20
PE15A3257	53	49
PE15A3258	53	50
PE15A3259	53	74
PE15A3260	53	84
PE15A3261	53	89
PE15A3262	52	35
PE15A3263	52	32
PE15A3264	52	34
PE15A3265	53	51
PE15A3266	53	90
PE15A3267	52	21
PE15A3268	53	85
PE15A3269	52	12
PE15A3270	53	54
PE15A3271	53	53
PE15A3272	52	14
PE15A3273	53	76
PE15A3274	53	82
PE15A3275	53	94
PE15A3276	52	36
PE15A3290	52	44
PE15A3291	52	45
PE15A3292	53	61
PE15A3293	53	63
PE15A3294	53	71
PE15A3295	53	68
PE15A3296	53	77
PE15A3300	56	3
PE15A3301	53	48
PE15A3302	53	72
PE15A3303	53	83
PE15A3304	53	87
PE15A3305	53	88
PE15A3306	53	92
PE15A3307	53	93
PE15A3308	52	7
PE15A3309	52	10
PE15A3310	52	9
PE15A3311	52	8
PE15A3312	52	16
PE15A3500	54	98
PE15A3501	Web	
PE15A3502	Web	
PE15A3503	52	43
PE15A3504	Web	
PE15A3505	53	67
PE15A3506	53	66
PE15A3507	53	79
PE15A3508	54	5
PE15A3509	54	6
PE15A3510	54	7
PE15A3511	54	8
PE15A3512	54	99
PE15A3513	54	1
PE15A3514	54	2
PE15A3515	54	3
PE15A3595	54	4
PE15A3900	54	95
PE15A3901	54	96
PE15A4001	53	64
PE15A4002	53	78
PE15A4003	52	39
PE15A4004	53

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE15A63012	56	6
PE15A63013	56	7
PE15A63014	56	8
PE15A63015	56	17
PE15A63016	56	12
PE15A63017	56	15
PE15A63018	56	11
PE15A63019	56	23
PE15A63020	56	16
PE15A63021	57	29
PE15A7000	61	82
PE15A7001	61	83
PE15A7002	61	84
PE15A7003	61	88
PE15A7004	61	89
PE15A7005	61	90
PE15A7006	61	91
PE15A7007	61	92
PE15A7008	61	94
PE15A7009	61	86
PE15A7010	61	86
PE15A7011	61	87
PE15A7012	61	93
PE15A8000	54	15
PE15A8001	54	12
PE15A8004	54	18
PE15A8005	54	19
PE15A8006	54	25
PE15A8007	54	26
PE15A86000	54	30
PE15A86001	54	29
PE15A86002	54	28
PE15A9001	Web	
PE15A9002	56	91
PE15B5000	52	3
PE15B5001	Web	
PE15B5003	52	1
PE15B5004	52	4
PE15B5005	52	5
PE15B5006	52	6
PE15B5007	52	2
PE15C5011F	Web	
PE15C5013	61	95
PE15C5013F	61	97
PE15C5014	61	1
PE15C5022	61	96
PE15C5022F	61	98
PE15G5060F	61	2
PE15G5068F	61	3
PE15J000	61	8
PE15J5011	61	4
PE15J5015	61	5
PE15K5000	61	6
PE15K5002	61	7
PE19XC7000	345	37
PE19XC7001	345	41
PE19XC7002	345	45
PE19XC7003	345	49
PE19XC7004	345	53
PE19XC7005	345	58
PE19XC7006	345	42
PE19XC7007	345	46
PE19XC7008	345	50
PE19XC7009	345	54
PE19XL6000	344	35
PE19XL6001	344	36
PE19XP5000	345	57
PE19XP5001	345	59
PE19XP5002	345	58
PE19XP5003	345	60
PE19XP5004	345	39
PE19XP5005	345	43
PE19XP5006	345	47
PE19XP5007	345	51
PE19XP5008	345	55
PE19XP5009	345	40
PE19XP5010	345	44
PE19XP5011	345	48
PE19XP5012	345	52
PE19XP5013	345	56
PE19XR1000	344	29
PE19XR1001	344	31
PE19XR1002	344	33
PE19XR1003	344	30
PE19XR1004	344	32
PE19XR1005	344	34
PE1BT1000	92	56
PE1BT1002	92	43
PE1V11000	341	36
PE1V11001	341	37
PE1V11002	341	38
PE1V11003	341	39
PE1V11004	342	40
PE1V11005	342	41
PE1V11006	342	42
PE1V11007	342	43
PE1V11008	342	44
PE1V11009	342	45
PE1V11010	342	46
PE1V11011	342	47
PE1V11012	342	48
PE1V11013	342	49
PE1V11014	342	50
PE1V11015	342	51
PE1V11016	342	52
PE1V11017	342	53
PE1V11018	342	54
PE1V11019	342	55
PE1V11020	342	56
PE1V11021	342	57
PE1V11022	342	58
PE1V11023	342	59
PE1V11024	342	60
PE1V11025	342	61
PE1V11026	342	62
PE1V11027	342	63
PE1V12000	343	77
PE1V12001	343	78
PE1V12002	343	79
PE1V12003	343	80
PE1V12004	343	81
PE1V12005	343	82
PE1V12006	343	83
PE1V12007	343	84
PE1V12008	343	85
PE1V13000	343	86
PE1V13001	343	87
PE1V13002	343	88
PE1V13003	343	89
PE1V13004	343	90
PE1V13005	343	91
PE1V13006	343	92
PE1V13007	343	93
PE1V13008	343	94
PE1V13009	343	95
PE1V13010	343	96
PE1V13011	343	97
PE1V13012	343	98
PE1V13013	343	99
PE1V13014	343	1
PE1V13015	343	2
PE1V14000	342	64
PE1V14001	342	65
PE1V14002	342	66
PE1V14003	342	67
PE1V14004	342	68
PE1V14005	342	69
PE1V14006	342	70
PE1V14007	342	71
PE1V14008	342	72
PE1V14009	342	73
PE1V14010	342	74
PE1V15000	342	75
PE1V15001	342	76
PE1V31000	Web	
PE1V31001	343	3
PE1V31002	343	4
PE1V31003	343	5
PE1V31004	Web	
PE1V31005	343	6
PE1V31006	Web	
PE1V31007	343	7
PE1V31008	Web	
PE1V31009	343	8
PE1V31010	343	9
PE1V31011	343	10
PE1V31013	Web	
PE1V31015	343	11
PE1V31016	343	12
PE1V31017	344	21
PE1V31018	343	13
PE1V31019	343	14
PE1V31020	344	22
PE1V31021	344	19
PE1V31022	344	20
PE1V31023	344	15
PE1V31024	344	23
PE1V31025	344	16
PE1V31026	344	17
PE1V31027	344	18
PE1V31028	344	24
PE1V31029	344	25
PE1V34000	344	26
PE1V34001	344	27
PE1V34002	Web	
PE1V34003	344	28
PE2000	324	40
PE2001	324	65
PE2002	Web	
PE2003	325	82
PE2004	324	66
PE2005	324	81
PE2006	324	77
PE2007	Web	
PE2008	325	83
PE2009	325	12
PE2011	325	92
PE2012	Web	
PE2014	325	95
PE2020	325	2
PE2021	325	22
PE2023	325	4
PE2024	Web	
PE2026	325	96
PE2027	Web	
PE2028	324	55
PE2029	325	18
PE2030	Web	
PE2032	324	45
PE2033	325	91
PE2034	Web	
PE2035	325	98
PE2036	324	57
PE2037	324	61
PE2038	324	67
PE2039	324	71
PE2040	324	73
PE2041	325	20
PE2043	Web	
PE2044	324	41
PE2045	Web	
PE2047	324	43
PE2048	326	35
PE2049	326	37
PE2050	311	66
PE2051	Web	
PE2052	311	72
PE2055	311	79
PE2056A	312	82
PE2057	312	83
PE2058	311	73
PE2059	311	76
PE2061	326	38
PE2062	326	36
PE2063	323	31
PE2064	324	33
PE2065	324	37
PE2066	324	34
PE2067	324	32
PE2068	324	35
PE2070	324	42
PE2074	325	90
PE2077	324	59
PE2078	324	58
PE2079A	324	60
PE2080	325	99
PE2081	324	56
PE2082	323	30
PE2083	324	38
PE2084	324	36
PE2088	325	88
PE2089	325	15
PE2090	325	9
PE2091	325	26
PE2092	325	87
PE2093	325	8
PE2094	325	14
PE2095	325	25
PE2200-10	308	39
PE2200-20	308	39
PE2200-30	308	39
PE2201-10	309	56
PE2201-30	309	58
PE2202-6	309	65
PE2202-10	Web	
PE2202-20	Web	
PE2202-30	309	65
PE2203-10	309	77
PE2203-20	309	79
PE2203-30	309	79
PE2204-6	309	80
PE2204-10	309	80
PE2204-20	309	80
PE2204-30	309	80
PE2205-20	309	89
PE2205-30	309	89
PE2206-6	309	92
PE2207-6	309	94
PE2207-10	309	94
PE2207-20	Web	
PE2207-30	309	96
PE2208-6	308	41
PE2208-10	308	43
PE2208-20	308	45
PE2209-6	309	60
PE2209-20	309	64
PE2210-6	309	67
PE2210-10	309	69
PE2210-20	309	71
PE2211-6	309	81
PE2211-10	309	81
PE2211-20	309	81
PE2212-10	Web	
PE2213-10	309	10
PE2215-6	309	72
PE2215-10	309	72
PE2215-20	309	76
PE2217-10	310	19
PE2217-20	310	19
PE2217-30	310	19
PE2218-10	310	21
PE2218-20	310	21
PE2218-30	310	21
PE2219-10	Web	
PE2219-20	310	22
PE2220-10	310	25
PE2220-20	310	25
PE2220-30	Web	
PE2221-10	310	26
PE2222-10	Web	
PE2222-30	310	27
PE2223-10	310	28
PE2223-20	310	28
PE2223-30	310	28
PE2224-30	310	29
PE2226-30	308	32
PE2227-30	Web	
PE2228A-30	308	33
PE2230-30	308	36
PE2234-30	Web	
PE2235-30	308	37
PE2236-35	308	35
PE2239-30	308	34
PE2240-30	308	25
PE2242A-06	Web	
PE2242-10	308	46
PE2242-20	308	46
PE2242A-20	308	47
PE2242A-30	Web	
PE2242-30	308	48
PE2243-10	309	49
PE2243-16	309	49
PE2243-20	309	49
PE2243-30	309	49
PE2DDV000	324	53
PE2DDV001	324	64
PE2DDV002	324	75
PE2DDV003	324	78
PE2DDV004	324	80
PE2DDV005	324	54
PE2DDV006	324	76
PE2DDV007	324	48
PE2DDV008	324	49
PE2DDV009	324	47
PE2DDV010	324	69
PE2DDV011	324	79
PE2DDV012	324	70
PE2DDV013	324	51
PE2DDV014	324	50
PE2DDV015	324	72
PE2DDV016	324	52
PE2DDV017	324	63
PE2DDV018	324	74
PE2DDV019	324	46
PE2DDV020	324	68
PE2DDV1026	345	65
PE2DDV1027	345	66
PE2DDV1028	345	67
PE2DDV1029	345	68
PE2DDV1030	345	69
PE2DDV1031	345	70
PE2DDV1032A	325	86
PE2DDV1033A	325	85
PE2DDV1034A	325	10
PE2DDV1036A	325	16
PE2DDV1038A	325	28
PE2DDV1039A	325	27
PE2DDV1040	324	62
PE2DDV1041	324	44
PE2DDV1044	323	21
PE2DDV1045	323	22
PE2DDV1046	323	26
PE2DDV1047	323	27
PE2DDV1048	323	28
PE2DDV1049	323	20
PE2DDV1050	323	24
PE2DDV1051	323	25
PE2DDV1052	323	29
PE2DDV1053	323	19
PE2DDV1056	324	39
PE2DDV1057	323	18
PE2DDV1058	325	93
PE2DDV1059	325	94
PE20DV1060	325	97
PE20DV1061	325	1
PE20DV1062	325	3
PE20DV1063	325	5
PE20DV1064	325	6
PE20DV1065	325	7
PE20DV1067	325	19
PE20DV1068	325	21
PE20DV1069	325	23
PE20DV1073	323	23
PE20DV2102	325	30
PE20DV2103	325	34
PE20DV2104	325	32
PE20DV2105	325	33
PE20DV2106	325	31
PE20S0001	326	39
PE20S0002	326	40
PE20S0003	326	41
PE20S0004	326	42
PE20S0005	326	43
PE20S0006	326	44
PE20S0007	326	45
PE20S0008	326	46
PE20S0009	326	47
PE20S0010	326	48
PE20S0011	326	49
PE20S0012	326	50
PE20S0013	326	51
PE20S0014	326	52
PE20S0015	326	53
PE20S0016	326	54
PE20S0017	326	55
PE20S0019	325	11
PE20S0020	325	17
PE20S0021	325	29
PE20S0022	325	84
PE20S0023	325	24
PE20S0024	325	13
PE20S0025	325	89
PE2BL1000	92	36
PE2BL1001	92	32
PE2BL1002	92	33
PE2BL1003	92	34
PE2BL1004	92	35
PE2BL1005	92	37
PE2BL1006	92	38
PE2CP000-10	309	73
PE2CP000-20	309	75
PE2CP000-30	309	85
PE2CP001-10	309	85
PE2CP001-20	309	85
PE2CP002-6	309	51
PE2CP002-10	309	51
PE2CP002-20	309	51
PE2CP003-6	308	40
PE2CP003-10	308	42
PE2CP003-20	308	44
PE2CP004-6	309	66
PE2CP004-10	309	68
PE2CP004-20	309	70
PE2CP005-6	309	59
PE2CP005-10	309	61
PE2CP005-20	309	63
PE2CP011	311	64
PE2CP013	311	68
PE2CP017	311	71
PE2CP019	311	75
PE2CP021	311	67
PE2CP023	311	74
PE2CP025-10	309	52
PE2CP1000	310	98
PE2CP1001	310	16
PE2CP1002	310	99
PE2CP1003	310	1
PE2CP1004	310	17
PE2CP1005	310	2
PE2CP1006	310	14
PE2CP1007	310	4
PE2CP1008	310	5
PE2CP1009	310	18
PE2CP1010	310	6
PE2CP1011	310	8
PE2CP1012	310	9
PE2CP1013	310	10
PE2CP1014	310	20
PE2CP1015	310	11
PE2CP1016	310	12
PE2CP1017	310	15
PE2CP1018	310	23
PE2CP1019	310	13
PE2CP1020	310	7
PE2CP1021	310	3
PE2CP1022	312	81
PE2CP1023-6	308	31
PE2CP1023-10	308	31
PE2CP1023-20	308	31
PE2CP1023-30	308	31
PE2CP1024-6	309	53
PE2CP1024-30	309	55
PE2CP1025-10	309	54
PE2CP1025-20	309	54
PE2CP1026	311	35
PE2CP1027	311	36
PE2CP1028	311	37
PE2CP1029	311	38
PE2CP1032	311	39
PE2CP1033	311	40
PE2CP1034	311	41
PE2CP1035	311	42
PE2CP1036	311	43
PE2CP1037	311	44
PE2CP1038	311	45
PE2CP1039	311	46
PE2CP1040	311	47
PE2CP1041	311	48
PE2CP1042	311	49
PE2CP1043	311	50
PE2CP1044	311	51
PE2CP1045	311	52
PE2CP1046	311	53
PE2CP1047	311	54
PE2CP1048	311	55
PE2CP1049	311	56
PE2CP1050	311	57
PE2CP1051	311	58
PE2CP1052	311	59
PE2CP1053	311	60
PE2CP1054	311	61
PE2CP1055	311	62
PE2CP1056	311	63
PE2CP1057	308	26
PE2CP1058	308	20
PE2CP1059	307	10
PE2CP1060	307	16
PE2CP1061	308	27
PE2CP1062	308	21
PE2CP1063	307	11
PE2CP1064	308	17
PE2CP1065	308	28
PE2CP1066	308	22
PE2CP1067	307	12
PE2CP1068	308	18
PE2CP1069	308	29
PE2CP1070	308	23
PE2CP1071	307	13
PE2CP1072	308	19
PE2CP1073	308	30
PE2CP1074	308	24
PE2CP1075	307	14
PE2CP1076	307	15
PE2CP1100	309	82
PE2CP1101	309	87
PE2CP1102	309	62
PE2CP1103	309	74
PE2CP1104	309	83
PE2CP1105	309	88
PE2CP1106	309	91
PE2CP1107	309	93
PE2CP1108	309	57
PE2CP1109	309	78
PE2CP1110	309	84
PE2CP1111	309	95
PE2CP1112	309	90
PE2CP1113	310	24
PE2CP1114-10	308	38
PE2CP1114-20	308	38
PE2CP1120-10	309	86
PE2CP1120-30	309	86
PE2CP1120-20	309	86
PE2CP1121-30	309	97
PE2CP1122-10	307	4
PE2CP1122-20	307	4
PE2CP1122-30	307	4
PE2CP1124-10	307	7
PE2CP1124-20	307	7
PE2CP1125-10	307	8
PE2CP1125-20	307	8
PE2CP1125-30	307	8
PE2CP1125-15	307	8
PE2CP1126-6	307	9
PE2CP1126-10	307	9
PE2CP1126-20	307	9
PE2CP1127-10	307	1
PE2CP1127-20	307	1
PE2CP1129-10	307	6
PE2CP1133-10	307	5
PE2CP1133-20	307	5
PE2CP1133-30	307	5
PE2CP1134-10	307	2
PE2CP1135-20	307	3
PE2CP1140	311	65
PE2CP1141	311	78
PE2CP1142	312	80
PE2CP1143	311	77
PE2CP1144	311	69
PE2CP1145	311	70
PE2CP1146	311	33
PE2CP1147	311	31
PE2CP1148	311	34
PE2CP1149	311	32
PE2CP1150	311	30
PE2CP1151	312	85
PE2CP1152	312	86
PE2CP1153	312	87
PE2CP1154	312	88
PE2CP1155	312	89
PE2CP1157	312	90
PE2CP1158	312	91
PE2CP1159	312	92
PE2CP1160	312	93
PE2CP1161	312	84
PE2PB1000	354	29
PE2PB1001	354	31
PE2PB1002	354	25
PE2PB1003	354	27
PE2PB1004	354	28
PE2PB1005	354	30
PE2PB1006	354	24
PE2PB1007	354	26
PE2V000	341	16
PE2V001	341	17
PE2V002	341	18
PE2V003	341	19
PE2V004	341	20
PE2V005	341	21
PE2V006	341	22
PE2V007	341	23
PE2V008	341	24
PE2V009	341	25
PE2V010	341	26
PE2V011	341	27
PE2V012	341	28
PE2V013	341	29
PE2V014	341	30
PE2V015	341	31
PE2V016	341	32
PE2V017	341	33
PE2V018	341	34
PE2V019	341	35
PE300	176	74
PE302	150	54
PE304	172	54
PE310-KIT	355	47
PE312	175	36
PE315	108	92
PE317	108	98
PE319	Web	
PE330	149	43
PE331	153	60
PE332	156	50
PE333	175	44
PE334	212	24
PE335	158	88
PE336	175	45
PE337	156	51
PE338	183	2
PE340	178	49
PE341	175	43
PE342	189	41
PE343	149	31
PE344	154	93
PE345	152	36
PE346	213	68
PE347	212	25
PE348	216	27
PE349	158	82
PE350	176	75
PE351	177	1
PE352	150	55
PE354	156	54
PE356	195	3
PE360	107	78
PE361	107	82
PE363	106	52
PE364	106	59
PE366	175	41
PE367	177	7
PE369	108	91
PE3000	Web	
PE3002	Web	
PE3003	178	29
PE3005	Web	
PE3010	Web	
PE3012	Web	
PE3013	173	90
PE3015	217	52
PE3016	Web	
PE3020	131	44
PE3023	211	7
PE3025	133	5
PE3027	Web	
PE3028	Web	
PE3030	Web	
PE3031	Web	
PE3034	155	8
PE3038	139	77
PE3041	222	79
PE3042	148	90
PE3044	134	6
PE3047	132	59
PE3049	Web	
PE3050	191	4
PE3051	180	4
PE3052	134	27
PE3056	179	67
PE3057	216	37
PE3058	183	78
PE3061	133	85
PE3062	Web	
PE3067	130	10
PE3069	Web	
PE3070	Web	
PE3071	152	28
PE3074	213	57
PE3075	131	35
PE3076	173	74
PE3078	179	64
PE3080	158	8
PE3081	131	36
PE3082	131	46
PE3083	139	76
PE3085	142	48
PE3087	130	19
PE3088	134	28
PE3089	184	29
PE3093	179	85
PE3094	134	31
PE3095	139	78
PE3097	148	95
PE3098	142	30
PE3100	223	80
PE3102	179	87
PE3103	132	82
PE3104	167	1
PE3107	142	57
PE3108	196	31
PE3109	223	81
PE3112	131	54
PE3116	168	20
PE3120	135	49
PE3121	176	66
PE3122	208	45
PE3123	Web	
PE3125	Web	
PE3126	Web	
PE3128	Web	
PE3130	203	98
PE3133	148	4
PE3134	208	48
PE3137	178	41
PE3138	176	77
PE3139	208	46
PE3141	190	87
PE3143	152	22
PE3145	139	66
PE3146	Web	
PE3147	190	76
PE3148	Web	
PE3149	191	2
PE3152	191	3
PE3154	184	9
PE3156	Web	
PE3157	208	49
PE3158	139	70
PE3160	179	74
PE3164	Web	
PE3166	202	76
PE3168	152	29
PE3170	148	5
PE3171	179	71
PE3172	181	44
PE3174	184	18
PE3176	184	16
PE3178	184	12
PE3179	189	35
PE3181	181	45
PE3182	139	67
PE3183	119	29
PE3184	180	2
PE3185	119	32
PE3187	181	51
PE3188	179	77
PE3189	119	30
PE3190	139	71
PE3192	119	35
PE3193	173	97
PE3194	214	1
PE3195	Web	
PE3197	Web	
PE3199	119	31
PE3200	139	69
PE3202	Web	
PE3205	119	37
PE3207	147	71
PE3209	Web	
PE3210	182	61
PE3211	139	68
PE3216	147	72
PE3217	155	12
PE3218	147	74
PE3221	168	41
PE3223	201	54
PE3224	168	42
PE3226	182	67
PE3227	155	18
PE3230	178	34
PE3231	216	44
PE3232	154	70
PE3233	168	44
PE3234	156	53
PE3236	201	64
PE3237	Web	
PE3238	Web	
PE3242	201	59
PE3244	204	33
PE3245	176	93
PE3252	148	89
PE3253	179	78
PE3254	148	98
PE3255	152	33
PE3258	143	59
PE3259	190	77
PE3263	143	60
PE3264	130	9
PE3265	143	61
PE3268	160	60
PE3269	143	62
PE3271	171	22
PE3272	160	55
PE3273	171	20
PE3274	Web	
PE3275	171	21
PE3277	Web	
PE3278	171	23
PE3280	148	9
PE3282	148	7
PE3285	148	8
PE3286	Web	
PE3287	Web	
PE3288	149	11
PE3290	141	8
PE3291	172	46
PE3295	140	7
PE3297	141	10
PE3299	141	21
PE3301	141	22
PE3302	172	52
PE3304	141	20
PE3306	141	23
PE3307	222	71
PE3309	141	13
PE3311	141	14
PE3312	Web	
PE3314	141	12
PE3316	141	15
PE3318	172	55
PE3319	177	19
PE3320	155	7
PE3321	172	47
PE3323	172	44
PE3325	131	51
PE3326	Web	
PE3327	131	43
PE3328	Web	
PE3333	179	86
PE3334	167	3
PE3335	Web	
PE3338	168	25
PE3340	139	83
PE3341	222	59
PE3343	135	47
PE3344	178	28
PE3345	173	91
PE3346	Web	
PE3347	190	66
PE3348	167	6
PE3349	201	60
PE3352	134	8
PE3362	178	44
PE3363	175	60
PE3365	131	50
PE3367	139	81
PE3368	132	58
PE3369	175	56
PE3370	134	11
PE3371	132	64
PE3372	Web	
PE3373	134	7
PE3374	Web	
PE3375	132	68
PE3376	223	86
PE3377	176	67
PE3378	133	4
PE3380	190	84
PE3381	134	9
PE3382	180	13
PE3383	Web	
PE3384	134	10
PE3385	175	59
PE3387	176	81
PE3388	223	87
PE3389	134	14
PE3390	Web	
PE3391	Web	
PE3393	178	35
PE3394	212	37
PE3395	167	4
PE3396	222	60
PE3398	222	62
PE3400	222	63
PE3402	213	60
PE3405	179	88
PE3407	161	75
PE3408	213	62
PE3409	167	5
PE3411	178	42
PE3412	160	61
PE3414	212	44
PE3416	167	8
PE3417	189	55
PE3418	212	35
PE3420	177	21
PE3421	212	42
PE3422	172	49
PE3423	132	81
PE3424	196	32
PE3425	212	39
PE3426	Web	
PE3427	132	78
PE3429	190	86
PE3431	131	31
PE3447	150	75
PE3448	172	42
PE3450	132	77
PE3451	142	58
PE3453	Web	
PE3455	150	68
PE3457	135	40
PE3458	134	15
PE3459	178	43
PE3462

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE3593	202	87
PE3594	204	23
PE3595	204	44
PE3596	204	46
PE3597	206	81
PE3598	206	83
PE3600	205	56
PE3601	205	58
PE3602	206	93
PE3604	134	29
PE3605	135	44
PE3606	132	65
PE3607	151	80
PE3608	212	48
PE3611	179	65
PE3612	222	68
PE3613	169	64
PE3614	172	53
PE3615	169	53
PE3616	222	69
PE3617	154	79
PE3620	Web	
PE3623	217	51
PE3627	132	67
PE3629	150	52
PE3631	Web	
PE3634	198	92
PE3635	217	54
PE3637	Web	
PE3642	188	11
PE3644	158	97
PE3646	189	58
PE3649	132	73
PE3650	154	71
PE3651	179	63
PE3652	158	93
PE3653	151	81
PE3654	172	68
PE3655	190	61
PE3656	176	80
PE3657	172	43
PE3661	158	92
PE3662	156	52
PE3664	184	11
PE3665	158	99
PE3666	158	4
PE3667	154	74
PE3669	183	79
PE3673	208	31
PE3675	135	35
PE3678	131	32
PE3679	191	19
PE3680	Web	
PE3681	188	13
PE3683	Web	
PE3684	212	30
PE3686	155	13
PE3689	131	52
PE3690	Web	
PE3693	Web	
PE3694	142	37
PE3695	Web	
PE3696	169	54
PE3697	179	69
PE3698	160	52
PE3699	152	21
PE3701	Web	
PE3704	176	70
PE3706	179	68
PE3713	190	70
PE3714	153	67
PE3715	179	66
PE3721	202	74
PE3722	181	49
PE3724	Web	
PE3726	152	23
PE3729	Web	
PE3733	187	8
PE3735	142	36
PE3736	182	64
PE3739	176	92
PE3740	192	27
PE3741	Web	
PE3743	217	58
PE3747	Web	
PE3749	130	17
PE3750	148	94
PE3753	Web	
PE3755	181	48
PE3758	195	24
PE3759	191	1
PE3764	198	89
PE3765	206	80
PE3767	Web	
PE3769	174	10
PE3775	190	63
PE3776	130	7
PE3777	132	60
PE3778	176	64
PE3779	177	25
PE3780	187	4
PE3781	160	56
PE3782	151	86
PE3785	Web	
PE3792	132	69
PE3794	198	77
PE3795	Web	
PE3796	217	55
PE3797	152	27
PE3799	180	9
PE3800	191	7
PE3803	216	41
PE3806	181	24
PE3807	130	8
PE3808	204	48
PE3809	182	68
PE3810	182	52
PE3814	176	90
PE3815	167	13
PE3816	134	12
PE3818	176	88
PE3819	190	82
PE3820	190	83
PE3821	178	40
PE3822	189	42
PE3823	179	83
PE3824	179	84
PE3825	180	18
PE3826	180	20
PE3827	151	87
PE3828	172	67
PE3829	154	90
PE3830	155	26
PE3832	179	70
PE3834	Web	
PE3835	180	6
PE3836	191	8
PE3838	Web	
PE3842	134	13
PE3843	167	15
PE3845	217	56
PE3850	187	3
PE3852	139	74
PE3853	202	71
PE3857	168	29
PE3858	190	85
PE3864	179	72
PE3865	177	22
PE3867	175	52
PE3869	Web	
PE3871	180	22
PE3874	148	99
PE3876	190	64
PE3882	160	57
PE3883	204	42
PE3884	Web	
PE3887	157	58
PE3894	Web	
PE3895	168	28
PE3898	216	38
PE3899	176	91
PE3902	204	43
PE3903	198	90
PE3904	211	6
PE3906	130	18
PE3907	Web	
PE3908	181	46
PE3911	172	48
PE3914	142	33
PE3915	202	77
PE3916	203	9
PE3917	203	15
PE3918	206	79
PE3919	206	85
PE3920	151	88
PE3921	154	91
PE3922	Web	
PE3924	180	7
PE3925	191	20
PE3928	Web	
PE3929	198	88
PE3930	223	99
PE3931	196	30
PE3932	198	85
PE3935	134	19
PE3940	180	21
PE3944	182	62
PE3945	Web	
PE3946	Web	
PE3948	Web	
PE3949	132	63
PE3950	142	46
PE3953	134	32
PE3954	Web	
PE3956	180	99
PE3957	172	51
PE3958	177	16
PE3959	180	3
PE3960	140	91
PE3961	180	97
PE3963	150	50
PE3965	153	66
PE3966	155	6
PE3967	181	23
PE3971	155	5
PE3973	187	70
PE3976	Web	
PE3977	154	78
PE3979	154	89
PE3982	158	3
PE3983	155	25
PE3986	154	76
PE3987	190	69
PE3988	154	86
PE3989	158	1
PE3991	158	98
PE3992	168	21
PE3993	155	28
PE3995	151	89
PE3996	153	68
PE3997	150	73
PE3999	130	11
PE33001	172	66
PE33002	Web	
PE33003	176	86
PE33004	Web	
PE33006	Web	
PE33009	Web	
PE33013	212	45
PE33014	189	34
PE33018	168	31
PE33021	161	76
PE33022	Web	
PE33024	Web	
PE33035	Web	
PE33039	Web	
PE33042	Web	
PE33046	Web	
PE33047	195	21
PE33053	217	53
PE33062	Web	
PE33064	Web	
PE33068	167	12
PE33069	Web	
PE33071	208	34
PE33073	193	49
PE33077	Web	
PE33084	198	82
PE33091	Web	
PE33098	135	48
PE33103	Web	
PE33112	Web	
PE33117	174	2
PE33120	195	19
PE33121	203	14
PE33123	131	39
PE33124	Web	
PE33125	Web	
PE33130	130	15
PE33132	Web	
PE33143	202	86
PE33144	147	77
PE33154	204	45
PE33155	Web	
PE33158	198	83
PE33159	Web	
PE33165	202	72
PE33174	Web	
PE33175	202	83
PE33176	198	94
PE33178	161	80
PE33179	219	10
PE33185	212	47
PE33188	219	93
PE33189	134	21
PE33191	200	40
PE33194	Web	
PE33196	219	2
PE33197	219	90
PE33208	Web	
PE33220	Web	
PE33221	Web	
PE33225	Web	
PE33236	150	74
PE33237	Web	
PE33243	Web	
PE33247	222	77
PE33253	Web	
PE33254	195	20
PE33257	187	6
PE33258	169	56
PE33261	203	21
PE33266	Web	
PE33267	217	57
PE33269	150	77
PE33270	222	76
PE33272	Web	
PE33275	Web	
PE33284	Web	
PE33285	Web	
PE33288	151	79
PE33300	Web	
PE33304	139	73
PE33307	Web	
PE33316	135	39
PE33318	Web	
PE33320	Web	
PE33321	152	34
PE33330	223	82
PE33342	Web	
PE33349	204	28
PE33350	203	10
PE33352	205	67
PE33355	Web	
PE33356	202	84
PE33361	184	14
PE33363	205	60
PE33367	Web	
PE33370	139	79
PE33377	150	57
PE33380	Web	
PE33381	Web	
PE33382	198	81
PE33384	Web	
PE33391	213	58
PE33393	Web	
PE33394	Web	
PE33396	184	22
PE33399	219	92
PE33400	Web	
PE33401	219	94
PE33405	219	95
PE33407	219	1
PE33412	219	4
PE33414	219	2
PE33417	219	9
PE33420	184	30
PE33421	219	11
PE33425	220	12
PE33426	220	21
PE33430	220	22
PE33432	220	23
PE33434	220	24
PE33437	219	6
PE33438	216	40
PE33440	Web	
PE33441	Web	
PE33442	Web	
PE33443	219	7
PE33445	219	8
PE33446	Web	
PE33448	220	25
PE33449	Web	
PE33450	220	26
PE33451	220	27
PE33452	Web	
PE33455	158	95
PE33456	220	28
PE33457	158	96
PE33469	Web	
PE33471	Web	
PE33476	203	16
PE33479	151	90
PE33481	173	96
PE33482	192	25
PE33484	Web	
PE33485	Web	
PE33488	Web	
PE33491	140	89
PE33494	Web	
PE33495	Web	
PE33502	201	53
PE33505	Web	
PE33510	Web	
PE33513	Web	
PE33516	142	51
PE33518	198	93
PE33519	169	60
PE33521	169	63
PE33523	169	58
PE33525	150	71
PE33527	150	70
PE33528	161	86
PE33529	Web	
PE33530	155	17
PE33532	161	85
PE33534	155	15
PE33535	211	4
PE33536	161	81
PE33537	140	90
PE33539	140	93
PE33541	140	88
PE33542	Web	
PE33543	155	11
PE33545	161	79
PE33546	Web	
PE33547	195	17
PE33548	Web	
PE33551	Web	
PE33552	Web	
PE33554	Web	
PE33555	173	98
PE33556	205	54
PE33557	Web	
PE33559	Web	
PE33561	Web	
PE33563	Web	
PE33565	Web	
PE33567	Web	
PE33574	131	38
PE33575	Web	
PE33580	205	66
PE33581	Web	
PE33583	139	80
PE33584	Web	
PE33586	223	83
PE33590	Web	
PE33596	Web	
PE33601	Web	
PE33603	Web	
PE33605	222	61
PE33615	158	90
PE33628	Web	
PE33632	Web	
PE33633	Web	
PE33634	Web	
PE33635	Web	
PE33641	204	40
PE33643	206	77
PE33644	222	78
PE33645	206	78
PE33646	223	84
PE33647	204	47
PE33649	206	84
PE33650	202	69
PE33652	202	70
PE33654	203	7
PE33656	203	8
PE33657	182	53
PE33658	205	52
PE33659	Web	
PE33660	205	53
PE33662	135	51
PE33668	205	59
PE33666	202	81
PE33668	202	82
PE33669	184	8
PE33670	202	88
PE33672	202	89
PE33673	184	15
PE33674	202	94
PE33675	204	27
PE33676	203	95
PE33680	Web	
PE33682	204	25
PE33686	205	68
PE33688	205	70
PE33690	205	72
PE33692	206	95
PE33698	Web	
PE33700	208	33
PE33701	211	99
PE33704	202	78
PE33706	167	17
PE33710	Web	
PE33714	Web	
PE33716	Web	
PE33720	150	65
PE33725	Web	
PE33728	154	75
PE33733	Web	
PE33737	Web	
PE33749	191	10
PE33751	Web	
PE33752	Web	
PE33753	Web	
PE33758	Web	
PE33759	193	50
PE33762	208	32
PE33764	Web	
PE33772	Web	
PE33774	Web	
PE33777	Web	
PE33778	139	82
PE33786	Web	
PE33789	198	87
PE33793	Web	
PE33795	Web	
PE33799	215	12
PE33801	Web	
PE33803	Web	
PE33825	201	62
PE33831	Web	
PE33837	202	67
PE33840	Web	
PE33844	173	89
PE33851	Web	
PE33853	Web	
PE33864	198	78
PE33867	213	69
PE33876	Web	
PE33887	Web	
PE33889	188	12
PE33896	179	82
PE33927	158	89
PE33928	184	6
PE33929	173	99
PE33938	140	84
PE33939	Web	
PE33948	184	21
PE33953	Web	
PE33954	Web	
PE33960	Web	
PE33964	195	15
PE33969	211	98
PE33974	160	51
PE33975	Web	
PE33977	160	48
PE33978	Web	
PE33982	Web	
PE33984	142	55
PE33989	169	65
PE33996	173	88
PE34008	169	51
PE34035	130	23
PE34036	Web	
PE34050	Web	
PE34057	Web	
PE34061	191	9
PE34062	Web	
PE34069	171	24
PE34070	198	79
PE34071	198	91
PE34078	206	91
PE34098	147	73
PE34106	Web	
PE34111	Web	
PE34116	181	27
PE34122	171	27
PE34123	Web	
PE34129	Web	
PE34134	Web	
PE34135	192	22
PE34138	151	84
PE34140	151	85
PE34141	191	6
PE34142	151	82
PE34143	174	7
PE34144	151	83
PE34146	150	44
PE34148	174	4
PE34149	150	45
PE34150	155	3
PE34151	174	6
PE34152	155	21
PE34153	173	86
PE34154	155	22
PE34155	174	8
PE34156	154	2
PE34157	174	9
PE34158	155	23
PE34159	174	5
PE34160	191	21
PE34161	155	24
PE34162	131	29
PE34163	173	87
PE34164	131	28
PE34166	130	5
PE34168	131	27
PE34169	174	12
PE34170	131	30
PE34171	173	92
PE34173	130	4
PE34174	173	93
PE34175	131	33
PE34176	173	94
PE34177	131	26
PE34178	174	3
PE34179	191	5
PE34180	176	83
PE34181	155	10
PE34182	176	85
PE34183	173	1
PE34184	176	82
PE34185	173	95
PE34186	175	47
PE34188	175	48
PE34191	176	78
PE34192	Web	
PE34193	176	79
PE34194	155	14
PE34195	178	37
PE34197	177	10
PE34198	155	16
PE34199	178	38
PE34200	178	36
PE34201	155	9
PE34202	177	11
PE34203	152	30
PE34204	178	32
PE34205	152	25
PE34206	178	33
PE34207	152	32
PE34208	190	79
PE34209	189	53
PE34210	152	31
PE34211	190	74
PE34212	152	26
PE34213	190	80
PE34214	161	85
PE34215	190	78
PE34216	163	28
PE34217	189	54
PE34218	161	78
PE34219	190	75
PE34220	178	39
PE34221	161	82
PE34222	160	58
PE34223	190	81
PE34224	179	75
PE34226	179	76
PE34227	161	84
PE34228	179	59
PE34229	161	77
PE34230	179	79
PE34231	160	53
PE34232	Web	
PE34233	179	60
PE34235	179	80
PE34236	160	59
PE34237	179	81
PE34238	160	54
PE34240	143	70
PE34241	180	10
PE34243	180	11
PE34244	Web	
PE34245	180	93
PE34246	184	19
PE34247	180	14
PE34248	184	13
PE34249	180	94
PE34250	184	31
PE34252	180	15
PE34253	184	20
PE34254	180	16
PE34255	184	33
PE34256	180	17
PE34257	172	61
PE34259	172	63
PE34261	172	62
PE34263	172	41
PE34265	172	64
PE34266	158	2
PE34268	171	40
PE34269	202	79
PE34270	172	65
PE34271	213	56
PE34272	158	94
PE34273	212	51
PE34274	154	72
PE34275	212	53
PE34276	154	73
PE34277	212	52
PE34279	213	54
PE34280	212	26
PE34281	154	77
PE34282	212	27
PE34283	153	69
PE34284	213	55
PE34285	154	88
PE34287	154	84
PE34289	154	87
PE34291	153	63
PE34292	195	16
PE34293	153	64
PE34296	154	85
PE34297	191	16
PE34299	191	98
PE34303	191	13
PE34305	191	14
PE34307	191	96
PE34309	191	11
PE34311	191	17
PE34312	Web	
PE34313	Web	
PE34315	191	18
PE34316	212	46
PE34317	191	15
PE34319	191	97
PE34321	191	12
PE34323	186	81
PE34324	Web	
PE34331	181	29
PE34351	188	33
PE34357	147	78
PE34359	147	79
PE34360	119	38
PE34361	186	75
PE34366	Web	
PE34370	Web	
PE34374	171	25
PE34383	Web	
PE34385	Web	
PE34387	Web	
PE34393	Web	
PE34396	185	50
PE34397	185	49
PE34398	181	32
PE34405	195	23
PE34406	184	26
PE34407	142	53
PE34408	184	23
PE34409	142	56
PE34410	184	24
PE34411	142	52
PE34412	184	4
PE34413	142	47
PE34414	184	27
PE34415	142	50
PE34416	184	7
PE34417	142	54
PE34418	184	28
PE34419	142	49
PE34420	184	25
PE34421	168	22
PE34422	184	5
PE34423	142	39
PE34424	168	26
PE34425	Web	
PE34427	142	34
PE34428	167	14
PE34429	142	32
PE34430	167	18
PE34431	142	35
PE34432	168	24
PE34433	142	40
PE34434	138	75
PE34435	135	52
PE34436	140	85
PE34437	135	45
PE34438	140	86
PE34439	167	2
PE34440	135	41
PE34441	167	10
PE34442	135	46
PE34443	167	99
PE34446	Web	
PE34447	167	7
PE34448	181	50
PE34449	167	11
PE34450	182	66
PE34452	182	54
PE34453	167	9
PE34454	182	70
PE34455	181	43
PE34456	182	69
PE34458	182	65
PE34459	206	87
PE34460	182	60
PE34461	203	17
PE34462	206	86
PE34463	203	12
PE34464	206	82
PE34465	203	18
PE34466	206	88
PE34467	203	22
PE34469	203	19
PE34470	206	92
PE34471	203	20
PE34472	206	97
PE34473	204	26
PE34474	206	98
PE34475	204	29
PE34476	206	89
PE34477	204	24
PE34478	206	90
PE34479	204	30
PE34480	206	96
PE34481	202	91
PE34482	206	99
PE34483	203	2
PE34484	206	94
PE34485	202	90
PE34486	206	1
PE34487	203	1
PE34488	202	68
PE34489	203	97
PE34490	202	80
PE34491	203	3
PE34492	205	55
PE34493	202	92
PE34494	205	50
PE34495	202	93
PE34496	205	62
PE34497	203	99
PE34498	205	74
PE34499	205	57
PE34500	205	69
PE34501	204	39
PE34502	205	51
PE34503	205	64
PE34504	210	91
PE34505	205	65
PE34507	205	71
PE34508	211	9
PE34509	205	63
PE34510	211	8
PE34511	205	73
PE34518	205	61
PE34520	214	87
PE34523	Web	
PE34532	Web	
PE34534	Web	
PE34536	Web	
PE34538	140	92
PE34539	Web	
PE34544	Web	
PE34548	Web	
PE34553	Web	
PE34554	159	16
PE34559	Web	
PE34562	Web	
PE34568	Web	
PE34570	108	96
PE34571	Web	
PE34572	108	94
PE34573	159	17
PE34574	108	97
PE34575	187	84
PE34576	108	95
PE34578	108	6
PE34579	216	45
PE34580	108	4
PE34581	216	36
PE34582	108	7
PE34583	216	39
PE34584	108	5
PE34585	216	43
PE34586	109	10
PE34587	217	48
PE34588	109	8
PE34589	216	42
PE34590	109	11
PE34591	217	46
PE34592	109	9
PE34595	Web	
PE34598	143	66
PE34599	143	67
PE34600	Web	
PE34604	Web	
PE34612	Web	
PE34614	181	28
PE34617	Web	
PE34618	Web	
PE34621	Web	
PE34622	Web	
PE34623	Web	
PE34626	159	22
PE34649	Web	
PE34666	149	16
PE34669	Web	
PE34670	Web	
PE34674	Web	
PE34675	Web	
PE34679	Web	
PE34680	160	47
PE34681	221	49
PE34683	221	50
PE34685	221	51
PE34686	197	65
PE34687	221	52
PE34689	221	53
PE34690	221	54
PE34691	Web	
PE34692	221	56
PE34693	149	13
PE34694	222	57
PE34696	222	58
PE34698	Web	
PE34701	221	46
PE34703	221	47
PE34704	Web	
PE34705	221	48
PE34707	Web	
PE34708	Web	
PE34709	198	76
PE34715	Web	
PE34716	153	43
PE34717	Web	
PE34721	204	49
PE34727	186	74
PE34729	107	81
PE34730	Web	
PE34731	107	80
PE34733	107	74
PE34739	Web	
PE34741	Web	
PE34742	Web	
PE34743	108	86
PE34745	108	85
PE34750	187	85
PE34752	Web	
PE34754	Web	
PE34755	Web	
PE34764	181	42
PE34770	186	80
PE34773	Web	
PE34777	171	29
PE34786	197	62
PE34792	Web	
PE34801	158	81
PE34808	Web	
PE34809	Web	
PE34812	Web	
PE34817	Web	
PE34831	Web	
PE34833	195	13
PE34834	196	28
PE34835	195	25
PE34836	195	27
PE34853	185	45
PE34854	185	46
PE34856	139	62
PE34858	139	63
PE34860	139	64
PE34862	139	59
PE34863	Web	
PE34864	139	60
PE34879	143	65
PE34881	143	74
PE34882	148	2
PE34883	143	75
PE34885	143	68
PE34887	171	26
PE34889	143	76
PE34891	143	69
PE34893	143	77
PE34895	143	78
PE34902	Web	
PE34917	195	22
PE34922	Web	
PE34925	Web	
PE34926	Web	
PE34945	Web	
PE34952	Web	
PE34957	188	14
PE34962	Web	
PE34966	159	15
PE34982	Web	
PE34990	Web	
PE35006	Web	
PE35012	Web	
PE35015	Web	
PE35021	217	50
PE35023	Web	
PE35024	Web	
PE35029	Web	
PE35035	Web	
PE35048	Web	
PE35051	Web	
PE35064	200	38
PE35087	Web	
PE35095	Web	
PE35097	Web	
PE35098	Web	
PE35100	Web	
PE35108	200	36
PE35109	169	52
PE35110	201	50
PE35111	Web	
PE35112	201	49
PE35114	200	37
PE35116	201	51
PE35118	201	52
PE35121	108	1
PE35131	Web	
PE35133	Web	
PE35144	Web	
PE35148	130	12
PE35154	200	35
PE35207	186	65
PE35208	181	30
PE35209	186	66
PE35210	181	31
PE35212	181	33
PE35213	186	68
PE35214	187	87
PE35216	187	88
PE35217	186	70
PE35218	187	89
PE35220	187	90
PE35221	186	76
PE35222	187	91
PE35223	186	77
PE35224	187	92
PE35225	186	78
PE35226	187	93
PE35227	186	79
PE35228	213	78
PE35229	214	84
PE35230	213	79
PE35231	214	85
PE35232	213	80
PE35233	214	86
PE35234	214	81
PE35235	214	88
PE35236	214	82
PE35238	214	83
PE35241	159	18
PE35242	185	47
PE35243	159	19
PE35244	185	48
PE35245	159	20
PE35246	185	51
PE35247	159	21
PE35256	130	95
PE35269	148	87
PE35276	148	6
PE35283	118	28
PE35284	147	70
PE35334	Web	
PE35347	189	43
PE35348	223	93
PE35349	187	94

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE35350	223	88
PE35351	181	35
PE35352	223	94
PE35353	187	95
PE35354	223	89
PE35355	181	36
PE35356	223	95
PE35357	187	96
PE35358	223	90
PE35359	181	37
PE35360	223	96
PE35361	187	97
PE35362	223	91
PE35363	181	38
PE35364	223	97
PE35365	187	98
PE35366	223	92
PE35367	181	39
PE35369	187	99
PE35371	181	40
PE35373	187	1
PE35375	181	41
PE35384	167	19
PE35387	Web	
PE35389	Web	
PE35404	198	80
PE35430	183	77
PE35435	Web	
PE35437	Web	
PE35441	Web	
PE35444	Web	
PE35454	Web	
PE35463	141	25
PE35474	Web	
PE35505	Web	
PE35508	186	82
PE35522	150	53
PE35527	182	55
PE35541	Web	
PE35556	Web	
PE35571	176	65
PE35573	Web	
PE35575	197	60
PE35580	131	42
PE35635	215	15
PE35646	Web	
PE35653	Web	
PE35654	Web	
PE35671	212	36
PE35672	Web	
PE35700	Web	
PE35711	212	34
PE35729	130	97
PE35751	Web	
PE35782	Web	
PE35784	174	25
PE35785	157	78
PE35787	Web	
PE35789	211	93
PE35791	Web	
PE35799	142	44
PE35815	Web	
PE35818	Web	
PE35843	Web	
PE35845	Web	
PE35874	130	98
PE35879	Web	
PE35882	Web	
PE35886	211	17
PE35894	Web	
PE35896	Web	
PE35900	119	34
PE35906	Web	
PE35907	Web	
PE35914	Web	
PE35916	Web	
PE35924	Web	
PE35934	Web	
PE35949	Web	
PE35953	138	54
PE35955	138	55
PE35957	138	56
PE35959	138	50
PE35962	138	51
PE35963	147	81
PE35965	147	69
PE35981	171	31
PE35991	193	53
PE35993	Web	
PE35997	211	16
PE36000	Web	
PE36012	Web	
PE36013	Web	
PE36028	Web	
PE36034	Web	
PE36046	Web	
PE36056	Web	
PE36058	183	96
PE36059	Web	
PE36064	Web	
PE36065	148	86
PE36066	130	94
PE36067	157	79
PE36068	210	88
PE36072	186	73
PE36101	Web	
PE36108	171	19
PE36109	218	78
PE36110	171	18
PE36111	218	79
PE36112	171	17
PE36113	218	80
PE36114	140	95
PE36115	Web	
PE36116	140	96
PE36117	218	81
PE36118	140	97
PE36119	218	82
PE36120	140	98
PE36121	Web	
PE36122	140	99
PE36123	218	86
PE36124	140	1
PE36125	218	87
PE36126	140	2
PE36127	218	83
PE36128	140	3
PE36129	218	84
PE36130	140	4
PE36131	218	85
PE36132	221	38
PE36134	119	33
PE36135	221	39
PE36136	119	36
PE36137	Web	
PE36138	119	39
PE36139	Web	
PE36140	118	26
PE36141	221	40
PE36142	119	40
PE36143	221	41
PE36144	118	27
PE36145	220	30
PE36146	207	13
PE36147	220	31
PE36148	207	9
PE36149	220	32
PE36150	207	14
PE36151	220	33
PE36152	207	10
PE36153	220	34
PE36154	207	19
PE36155	220	35
PE36156	207	15
PE36157	168	40
PE36158	207	20
PE36159	168	43
PE36160	207	16
PE36161	169	45
PE36162	207	6
PE36163	169	46
PE36164	182	71
PE36165	169	47
PE36166	182	72
PE36167	169	48
PE36168	207	7
PE36169	168	38
PE36170	147	75
PE36171	169	49
PE36172	147	76
PE36173	168	39
PE36174	120	81
PE36178	147	68
PE36181	151	92
PE36182	Web	
PE36200	171	32
PE36201	178	46
PE36203	Web	
PE36209	Web	
PE36215	Web	
PE36219	130	96
PE36227	Web	
PE36228	Web	
PE36236	Web	
PE36246	Web	
PE36265	Web	
PE36266	Web	
PE36269	Web	
PE36273	150	69
PE36283	159	23
PE36292	Web	
PE36298	Web	
PE36303	Web	
PE36305	Web	
PE36307	Web	
PE36322	Web	
PE36325	Web	
PE36345	134	26
PE36362	159	14
PE36376	Web	
PE36380	Web	
PE36381	Web	
PE36384	Web	
PE36417	180	90
PE36419	Web	
PE36433	Web	
PE36440	Web	
PE36444	Web	
PE36452	Web	
PE36455	134	30
PE36472	Web	
PE36475	177	96
PE36491	Web	
PE36504	Web	
PE36507	188	19
PE36517	Web	
PE36519	104	17
PE36520	124	58
PE36521	104	13
PE36522	124	59
PE36523	104	18
PE36524	124	60
PE36525	104	14
PE36526	124	61
PE36528	124	62
PE36530	124	63
PE36532	124	67
PE36534	124	68
PE36535	108	90
PE36536	124	69
PE36537	108	89
PE36539	168	34
PE36540	124	65
PE36541	168	32
PE36546	Web	
PE36551	Web	
PE36555	211	15
PE36562	Web	
PE36569	208	35
PE36570	208	38
PE36571	208	36
PE36572	208	39
PE36573	208	37
PE36574	208	40
PE36589	150	67
PE36593	Web	
PE36605	Web	
PE36613	Web	
PE36623	Web	
PE36634	149	15
PE36657	119	52
PE36661	169	59
PE36667	Web	
PE36680	Web	
PE36689	175	57
PE36690	175	58
PE36701	Web	
PE36735	Web	
PE36737	Web	
PE36738	143	81
PE36755	Web	
PE36773	Web	
PE36776	Web	
PE36779	215	22
PE36780	Web	
PE36784	Web	
PE36789	Web	
PE36799	141	11
PE36805	Web	
PE36839	Web	
PE36848	184	32
PE36874	Web	
PE36878	Web	
PE36897	Web	
PE36910	159	30
PE36919	Web	
PE36939	Web	
PE36955	Web	
PE36958	158	80
PE36963	181	34
PE36970	Web	
PE36971	Web	
PE36982	Web	
PE37009	Web	
PE37007	Web	
PE37019	Web	
PE37028	Web	
PE37061	Web	
PE37067	Web	
PE37080	Web	
PE37091	Web	
PE37099	141	24
PE37109	Web	
PE37112	Web	
PE37113	Web	
PE37120	185	44
PE37137	213	77
PE37140	Web	
PE37151	Web	
PE37163	221	37
PE37175	Web	
PE37176	Web	
PE37185	Web	
PE37220	Web	
PE37250	201	65
PE37257	Web	
PE37275	Web	
PE37294	Web	
PE37299	Web	
PE37301	Web	
PE37305	Web	
PE37321	Web	
PE37332	Web	
PE37357	158	91
PE37362	Web	
PE37364	Web	
PE37378	Web	
PE37401	183	80
PE37411	Web	
PE37425	Web	
PE37432	Web	
PE37434	Web	
PE37450	120	70
PE37455	Web	
PE37478	211	5
PE37497	121	4
PE37512	Web	
PE37513	Web	
PE37563	210	90
PE37567	Web	
PE37573	Web	
PE37580	184	10
PE37589	Web	
PE37594	210	89
PE37600	119	51
PE37610	Web	
PE37640	134	17
PE37642	Web	
PE37693	Web	
PE37697	Web	
PE37747	Web	
PE37749	Web	
PE37808	219	91
PE37811	Web	
PE37812	Web	
PE37821	Web	
PE37828	Web	
PE37840	174	13
PE37841	195	5
PE37842	138	57
PE37843	139	65
PE37844	129	93
PE37845	135	36
PE37846	143	63
PE37847	143	64
PE37848	165	66
PE37849	215	6
PE37850	155	30
PE37851	162	10
PE37859	211	3
PE37885	210	87
PE37900	181	25
PE37908	174	24
PE37920	Web	
PE37940	149	12
PE37941	149	14
PE37942	149	17
PE37943	149	18
PE37944	151	95
PE37945	151	96
PE37946	151	97
PE37947	151	98
PE37948	153	41
PE37949	153	42
PE37950	153	44
PE37951	153	45
PE37952	118	17
PE37953	118	18
PE37954	118	19
PE37955	118	20
PE37956	119	41
PE37957	119	42
PE37958	119	43
PE37959	Web	
PE37960	119	54
PE37961	119	55
PE37962	119	56
PE37963	119	57
PE37969	154	81
PE37970	152	37
PE37972	120	71
PE37973	119	53
PE37980	Web	
PE37995	178	45
PE38012	Web	
PE38023	Web	
PE38040	Web	
PE38052	195	9
PE38059	176	94
PE38083	Web	
PE38089	Web	
PE38093	187	2
PE38116	174	14
PE38117	Web	
PE38130	Web	
PE38132	Web	
PE38133	Web	
PE38134	Web	
PE38135	Web	
PE38136	Web	
PE38137	Web	
PE38138	Web	
PE38139	Web	
PE38140	Web	
PE38141	Web	
PE38147	Web	
PE38161	166	72
PE38184	198	84
PE38192	Web	
PE38194	159	32
PE38202	Web	
PE38204	Web	
PE38207	Web	
PE38208	Web	
PE38215	Web	
PE38231	143	72
PE38240	179	89
PE38249	134	16
PE38268	Web	
PE38270	166	71
PE38271	165	70
PE38272	165	67
PE38273	174	16
PE38274	174	17
PE38275	174	15
PE38276	195	8
PE38277	195	7
PE38278	195	6
PE38291	Web	
PE38296	218	67
PE38298	217	63
PE38299	199	15
PE38300	200	26
PE38301	200	34
PE38302	217	64
PE38303	216	34
PE38304	216	30
PE38311	Web	
PE38314	Web	
PE38318	Web	
PE38322	143	73
PE38343	221	42
PE38344	132	56
PE38351	Web	
PE38355	Web	
PE38364	Web	
PE38387	Web	
PE38392	Web	
PE38402	Web	
PE38407	208	41
PE38423	Web	
PE38433	171	30
PE38436	147	64
PE38438	Web	
PE38446	167	92
PE38447	167	93
PE38448	167	91
PE38449	167	90
PE38450	156	36
PE38451	156	37
PE38452	156	35
PE38453	156	34
PE38454	163	13
PE38455	163	14
PE38456	162	12
PE38457	162	11
PE38465	Web	
PE38485	167	95
PE38486	167	94
PE38487	167	96
PE38488	167	97
PE38489	156	40
PE38490	156	38
PE38491	156	41
PE38492	156	42
PE38493	163	16
PE38494	163	15
PE38495	163	17
PE38496	163	18
PE38502	217	62
PE38506	134	18
PE38511	Web	
PE38515	Web	
PE38533	Web	
PE38543	Web	
PE38547	Web	
PE38574	191	91
PE38584	119	50
PE38589	Web	
PE38603	Web	
PE38624	177	97
PE38627	Web	
PE38628	174	26
PE38632	217	49
PE38638	178	47
PE38642	183	97
PE38644	Web	
PE38645	171	33
PE38651	Web	
PE38670	161	74
PE38671	Web	
PE38672	154	92
PE38674	216	35
PE38679	143	71
PE38699	159	31
PE38700	Web	
PE38714	Web	
PE38719	138	53
PE38725	Web	
PE38740	Web	
PE38746A	137	21
PE38746B	137	23
PE38746C	137	24
PE38746D	137	25
PE38746H	137	26
PE38746I	137	27
PE38746K	137	28
PE38746Z	137	22
PE38747A	135	55
PE38747B	Web	
PE38747C	135	56
PE38747D	135	57
PE38747H	135	58
PE38747I	135	59
PE38747K	136	60
PE38747Z	136	61
PE38748A	136	76
PE38748B	Web	
PE38748C	136	77
PE38748D	136	78
PE38748H	136	79
PE38748I	136	80
PE38748K	136	81
PE38748Z	136	82
PE38749A	137	98
PE38749B	137	99
PE38749C	137	1
PE38749D	137	2
PE38749H	137	3
PE38749I	137	4
PE38749K	137	5
PE38749Z	137	6
PE38750A	137	29
PE38750B	137	30
PE38750C	137	31
PE38750D	137	32
PE38750H	138	33
PE38750I	138	34
PE38750K	138	35
PE38750Z	138	36
PE38751A	136	62
PE38751B	Web	
PE38751C	136	63
PE38751D	136	64
PE38751H	136	65
PE38751I	136	66
PE38751K	136	67
PE38751Z	136	68
PE38752A	136	83
PE38752B	Web	
PE38752C	136	84
PE38752D	136	85
PE38752H	136	86
PE38752I	136	87
PE38752K	136	88
PE38752Z	136	89
PE38753A	137	7
PE38753B	Web	
PE38753C	137	8
PE38753D	137	9
PE38753H	137	10
PE38753I	137	11
PE38753K	137	12
PE38753Z	137	13
PE38754A	138	38
PE38754B	138	39
PE38754C	138	40
PE38754D	138	41
PE38754H	138	42
PE38754I	138	43
PE38754K	138	44
PE38754Z	138	45
PE38755A	136	69
PE38755B	Web	
PE38755C	136	70
PE38755D	136	71
PE38755H	136	72
PE38755I	136	73
PE38755K	136	74
PE38755Z	136	75
PE38756A	136	90
PE38756B	136	91
PE38756C	136	92
PE38756D	136	93
PE38756H	136	94
PE38756I	136	95
PE38756K	136	96
PE38756Z	136	97
PE38757A	137	14
PE38757B	Web	
PE38757C	137	15
PE38757D	137	16
PE38757H	137	17
PE38757I	137	18
PE38757K	137	19
PE38757Z	138	49
PE38762	Web	
PE38772	Web	
PE38781	Web	
PE38795	Web	
PE38804	132	71
PE38813	159	24
PE38826	Web	
PE38830	212	32
PE38838	Web	
PE38842	Web	
PE38853	Web	
PE38858	138	58
PE38881	185	57
PE38889	Web	
PE38890	217	61
PE38898	Web	
PE38907	Web	
PE38920	189	44
PE38927	Web	
PE38930	217	66
PE38934	151	94
PE38943	Web	
PE38953	Web	
PE38997	131	40
PE39035	206	3
PE39051	Web	
PE39061	Web	
PE39074	Web	
PE39078	217	65
PE39081	Web	
PE39082	161	73
PE39087	175	55
PE39108	131	55
PE39112	Web	
PE39113	Web	
PE39118	Web	
PE39120	203	6
PE39138	187	9
PE39143	147	63
PE39148	178	48
PE39171	Web	
PE39185	133	3
PE39197A	Web	
PE39197B	Web	
PE39197C	170	79
PE39197D	170	80
PE39197H	170	81
PE39197I	170	82
PE39197K	170	83
PE39197Z	170	84
PE39199A	170	1
PE39199B	170	2
PE39199C	170	3
PE39199D	170	4
PE39199H	170	5
PE39199I	170	6
PE39199K	170	7
PE39199Z	170	8
PE39229	168	27
PE39255	211	96
PE39258	Web	
PE39260	Web	
PE39275	Web	
PE39277	Web	
PE39278	Web	
PE39298	Web	
PE39301	Web	
PE39315	Web	
PE39318	Web	
PE39333	Web	
PE39342A	169	71
PE39342B	169	72
PE39342C	169	73
PE39342D	169	74
PE39342H	170	75
PE39342I	170	76
PE39342K	170	77
PE39342Z	170	78
PE39343A	170	85
PE39343B	Web	
PE39343C	170	86
PE39343D	170	87
PE39343H	170	88
PE39343I	170	89
PE39343K	170	90
PE39343Z	170	91
PE39344A	193	56
PE39344B	Web	
PE39344C	193	57
PE39344D	193	58
PE39344H	193	59
PE39344I	193	60
PE39344K	193	61
PE39344Z	193	62
PE39345A	193	63
PE39345B	Web	
PE39345C	193	64
PE39345D	193	65
PE39345H	193	66
PE39345I	193	67
PE39345K	194	68
PE39345Z	194	69
PE39346A	194	70
PE39346B	Web	
PE39346C	194	71
PE39346D	194	72
PE39346H	194	73
PE39346I	194	74
PE39346K	194	75
PE39346Z	194	76
PE39347A	170	92
PE39347B	170	93
PE39347C	170	94
PE39347D	170	95
PE39347H	170	96
PE39347I	170	97
PE39347K	170	98
PE39347Z	170	99
PE39348A	170	9
PE39348B	170	10
PE39348C	170	11
PE39348D	170	12
PE39348H	170	13
PE39348I	171	14
PE39348K	171	15
PE39348Z	171	16
PE39349A	194	77
PE39349B	194	78
PE39349C	194	79
PE39349D	194	80
PE39349H	194	81
PE39349I	194	82
PE39349K	194	83
PE39349Z	194	84
PE39350A	194	85
PE39350B	194	86
PE39350C	194	87
PE39350D	194	88
PE39350H	194	89
PE39350I	194	90
PE39350K	194	91
PE39350Z	194	93
PE39351A	194	94
PE39351B	194	95
PE39351C	194	96
PE39351D	194	97
PE39351H	194	98
PE39351I	194	99
PE39351K	194	99
PE39351Z	138	47
PE39395	185	55
PE39401	Web	
PE39415	175	53
PE39416	189	59
PE39417	177	15
PE39418	178	53
PE39419	180	96
PE39420	191	99
PE39421	197	58
PE39422	144	86
PE39423	175	50
PE39424	189	56
PE39425	177	13
PE39426	178	52
PE39427	197	68
PE39428	191	93
PE39429	175	54
PE39430	190	60
PE39431	189	38
PE39432	178	54
PE39433	180	98
PE39434	197	73
PE39435	197	59
PE39436	197	61
PE39437	175	51
PE39438	189	57
PE39439	177	14
PE39440	179	62
PE39441	180	95
PE39442	191	94
PE39443	150	49
PE39444	160	37
PE39445	151	9
PE39446	153	49
PE39447	173	83
PE39448	188	31
PE39449	163	23
PE39450	144	83
PE39451	150	48
PE39452	160	49
PE39453	151	8
PE39454	153	48
PE39455	173	81
PE39456	188	28
PE39457	150	51
PE39458	160	38
PE39459	152	10
PE39460	162	2
PE39461	173	84
PE39462	188	32
PE39463	163	24
PE39464	163	25
PE39465	149	35
PE39466	160	50
PE39467	152	20
PE39468	162	3
PE39469	173	82
PE39470	188	29
PE39471	212	23
PE39472	214	96
PE39473	214	92
PE39474	214	71
PE39475	185	39
PE39476	193	46
PE39477	215	10
PE39478	215	13
PE39479	212	22
PE39480	214	98
PE39481	213	65
PE39482	215	8
PE39483	185	41
PE39484	193	44
PE39485	212	31
PE39486	214	97
PE39487	213	67
PE39488	213	72
PE39489	185	40
PE39490	193	48
PE39491	215	11
PE39492	215	14
PE39493	212	29
PE39494	214	99
PE39495	213	66
PE39496	213	73
PE39497	185	42
PE39498	193	45
PE39520	Web	
PE39521	Web	
PE39547	Web	
PE39548	Web	
PE39564	171	28
PE39571	Web	
PE39619	Web	
PE39651	Web	
PE39660	Web	
PE39667	Web	
PE39701	Web	
PE39702	Web	
PE39707	Web	
PE39710	Web	
PE39719	Web	
PE39723	Web	
PE39727	Web	
PE39755	Web	
PE39809	Web	
PE39869	Web	
PE39884	Web	
PE39968	Web	
PE39970	Web	
PE39991	Web	
PE3C0031	158	84
PE3C0033	149	22
PE3C0038	174	20
PE3C0039	149	19
PE3C0040	169	70
PE3C0041	151	99
PE3C0042	211	20
PE3C0044	171	35
PE3C0045	195	11
PE3C0046	149	23
PE3C0047	211	10
PE3C0048	149	25
PE3C0049	156	32
PE3C0050	151	4
PE3C0051	169	50
PE3C0052	174	29
PE3C0053	149	20
PE3C0054	130	24
PE3C0056	193	41
PE3C0057	174	18
PE3C0058	213	63
PE3C0059	156	39
PE3C0060	149	29
PE3C0061	149	30
PE3C0062	149	26
PE3C0063	165	57
PE3C0064	201	48
PE3C0101	149	21
PE3C0102	172	59
PE3C0103	175	30
PE3C0104	177	99
PE3C0105	149	24
PE3C0106	151	1
PE3C0107	159	33
PE3C0109	158	85
PE3C0110	149	27
PE3C0111	151	5
PE3C0112	149	28
PE3C0113	174	19
PE3C0117	212	21
PE3C0118	150	62
PE3C0119	160	34
PE3C0120	159	29
PE3C0121	172	58
PE3C0124-12	102	48
PE3C0125	153	62
PE3C0126	162	7
PE3C0218	150	60
PE3C0230	174	27
PE3C0231	149	32
PE3C0252	172	56
PE3C0253	156	45
PE3C0377	102	46
PE3C0438	207	17
PE3C0441	104	3
PE3C0481	186	72
PE3C0643	201	43
PE3C0643-3	159	99
PE3C0666	107	76
PE3C0673	161	67
PE3C0688	171	34
PE3C0752	104	15
PE3C0757	207	12
PE3C0780	184	34
PE3C0806	177	2
PE3C0835	107	66
PE3C0847	183	98
PE3C0967	160	35
PE3C1000	163	29
PE3C1015	176	84
PE3C1037	172	69
PE3C1041	214	90
PE3C1057	197	52
PE3C1057-3	359	90
PE3C1081	197	66
PE3C1084	164	44
PE3C1110	164	42
PE3C1128	157	63
PE3C1144	214	94
PE3C1173	193	42
PE3C1179	192	36
PE3C1203	190	72
PE3C1239	195	12
PE3C1271	162	97
PE3C1377	107	75
PE3C1409	192	39
PE3C1425	189	45
PE3C1528	188	22
PE3C1545	201	56
PE3C1545-3	359	91
PE3C1617	192	38
PE3C1722	177	8
PE3C1830	169	66
PE3C1876	179	73
PE3C1982	156	56
PE3C1988	205	75
PE3C2000	149	39
PE3C2001	153	51
PE3C2002	147	67
PE3C2003	118	23
PE3C2004	120	59
PE3C2005	148	84
PE3C2006	156	47
PE3C2007	168	37
PE3C2008	175	38
PE3C2009	109	16
PE3C2010	109	19
PE3C2011	149	38
PE3C2012	147	66
PE3C2013	118	22
PE3C2014	147	83
PE3C2015	120	58
PE3C2034	130	16
PE3C2035	169	57
PE3C2162	173	80
PE3C2180	216	28
PE3C2220	130	99
PE3C2276	159	12
PE3C2295	130	14
PE3C2305	190	88
PE3C2360	169	62
PE3C2404	148	88
PE3C2416	130	21
PE3C2449	185	38
PE3C2578	204	35
PE3C2599	204	36
PE3C2884	189	52
PE3C2892	180	19
PE3C2897	102	49
PE3C2953	161	72
PE3C2985	188	27
PE3C3028	182	74
PE3C3055	174	21
PE3C3115	161	65
PE3C3159	195	4
PE3C3205	196	46
PE3C3221	207	22
PE3C3232	163	31
PE3C3233	161	46
PE3C3234	162	6
PE3C3235	175	46
PE3C3236	172	70
PE3C3237	173	77
PE3C3238	188	20
PE3C3240	152	19
PE3C3241	153	61
PE3C3242	183	3
PE3C3243	162	94

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE3C3244	163	22
PE3C3245	188	30
PE3C3246	173	85
PE3C3247	162	8
PE3C3248	177	9
PE3C3249	188	24
PE3C3250	188	26
PE3C3251	172	71
PE3C3252	173	78
PE3C3255	155	19
PE3C3275	124	64
PE3C3286	155	27
PE3C3314	134	22
PE3C3318	201	61
PE3C3321	169	69
PE3C3325	132	61
PE3C3328	169	55
PE3C3332	186	67
PE3C3344	132	66
PE3C3349	131	37
PE3C3350	187	10
PE3C3354	172	57
PE3C3375	131	48
PE3C3377	131	49
PE3C3378	148	92
PE3C3379	148	93
PE3C3380	148	97
PE3C3387	140	5
PE3C3391	131	53
PE3C3393	211	2
PE3C3397	132	75
PE3C3399	132	76
PE3C3400	211	95
PE3C3401	211	97
PE3C3404	131	47
PE3C3409	139	61
PE3C3412	186	69
PE3C3413	186	71
PE3C3414	214	89
PE3C3420	138	52
PE3C3424	214	66
PE3C3425	204	34
PE3C3428	201	63
PE3C3437	187	7
PE3C3446	132	80
PE3C3448	187	5
PE3C3453	132	62
PE3C3469	104	2
PE3C3583	133	1
PE3C3643	152	40
PE3C3821	197	63
PE3C3854	144	5
PE3C3922	145	16
PE3C3937	198	98
PE3C3985	144	89
PE3C3986	144	93
PE3C3987	145	30
PE3C3989	144	3
PE3C3990	146	39
PE3C3991	146	20
PE3C3992	146	56
PE3C3993	144	97
PE3C3994	146	34
PE3C3995	145	25
PE3C3996	147	60
PE3C3997	145	7
PE3C3998	146	43
PE3C3999	145	11
PE3C4000	147	80
PE3C4000-60	357	56
PE3C4000-144	357	56
PE3C4001	148	85
PE3C4001-60	357	57
PE3C4001-144	357	57
PE3C4002	150	58
PE3C4002-60	357	58
PE3C4002-144	357	58
PE3C4003	152	38
PE3C4003-60	357	59
PE3C4003-144	357	59
PE3C4004	154	82
PE3C4004-60	357	60
PE3C4004-144	357	60
PE3C4005	150	59
PE3C4005-100CM	357	61
PE3C4006	152	39
PE3C4006-100CM	357	62
PE3C4007	154	83
PE3C4007-100CM	357	63
PE3C4008	156	55
PE3C4008-60	357	64
PE3C4009	157	65
PE3C4009-60	357	65
PE3C4010	158	5
PE3C4010-60	357	66
PE3C4011	159	11
PE3C4011-60	357	67
PE3C4012	108	3
PE3C4012-100CM	357	68
PE3C4013	109	13
PE3C4013-100CM	357	69
PE3C4014	144	90
PE3C4015	144	94
PE3C4016	146	31
PE3C4017	145	17
PE3C4018	146	53
PE3C4019	144	4
PE3C4020	146	40
PE3C4021	145	21
PE3C4022	147	57
PE3C4023	144	98
PE3C4024	146	35
PE3C4025	146	26
PE3C4026	147	61
PE3C4027	145	8
PE3C4028	146	44
PE3C4029	145	12
PE3C4030	146	48
PE3C4031	144	88
PE3C4032	144	92
PE3C4033	145	29
PE3C4034	145	15
PE3C4035	146	51
PE3C4036	144	2
PE3C4037	146	38
PE3C4038	145	19
PE3C4039	146	55
PE3C4040	144	96
PE3C4041	146	33
PE3C4042	145	24
PE3C4043	147	59
PE3C4044	145	6
PE3C4045	146	42
PE3C4046	145	10
PE3C4047	146	46
PE3C4048	144	91
PE3C4049	144	95
PE3C4050	146	32
PE3C4051	145	18
PE3C4052	146	54
PE3C4053	146	41
PE3C4054	145	22
PE3C4055	147	58
PE3C4056	144	99
PE3C4057	146	36
PE3C4058	145	27
PE3C4059	147	62
PE3C4060	145	9
PE3C4061	146	45
PE3C4062	145	13
PE3C4063	146	49
PE3C4064	144	87
PE3C4065	145	28
PE3C4066	145	14
PE3C4067	146	50
PE3C4068	144	1
PE3C4069	146	37
PE3C4130-100CM	102	18
PE3C4131	122	10
PE3C4132	102	29
PE3C4133	121	87
PE3C4134-100CM	102	3
PE3C4135-100CM	102	10
PE3C4136	147	82
PE3C4137-100CM	102	30
PE3C4138	153	52
PE3C4139	151	93
PE3C4140	102	27
PE3C4141-100CM	102	28
PE3C4142-100CM	102	7
PE3C4143-100CM	102	1
PE3C4144	122	14
PE3C4145	160	42
PE3C4146	115	53
PE3C4147	115	48
PE3C4164	183	1
PE3C4238	163	32
PE3C4341	207	11
PE3C4374	209	70
PE3C4386	126	14
PE3C4388	209	53
PE3C4389	209	60
PE3C4390	210	82
PE3C4391	183	83
PE3C4392	183	95
PE3C4393	196	36
PE3C4394	196	42
PE3C4395	199	2
PE3C4396	199	10
PE3C4397	133	91
PE3C4398	133	99
PE3C4399	157	69
PE3C4400	157	77
PE3C4401	209	64
PE3C4402	210	85
PE3C4403	209	54
PE3C4404	209	58
PE3C4405	183	85
PE3C4406	183	91
PE3C4407	192	30
PE3C4408	192	33
PE3C4409	196	37
PE3C4410	196	40
PE3C4411	199	3
PE3C4412	199	7
PE3C4413	133	92
PE3C4414	133	96
PE3C4415	157	70
PE3C4416	157	74
PE3C4417	209	65
PE3C4418	210	78
PE3C4419	209	51
PE3C4420	209	55
PE3C4421	209	67
PE3C4422	183	81
PE3C4423	183	87
PE3C4424	192	28
PE3C4425	192	31
PE3C4426	196	35
PE3C4427	196	38
PE3C4428	198	99
PE3C4429	199	4
PE3C4430	133	89
PE3C4431	133	93
PE3C4432	157	67
PE3C4433	157	71
PE3C4434	209	62
PE3C4435	210	75
PE3C4437	183	86
PE3C4441	209	52
PE3C4442	209	59
PE3C4443	210	81
PE3C4444	183	82
PE3C4445	183	94
PE3C4446	192	29
PE3C4447	192	35
PE3C4448	198	1
PE3C4449	199	9
PE3C4450	133	90
PE3C4451	157	68
PE3C4452	157	76
PE3C4453	209	63
PE3C4454	210	84
PE3C4455	209	57
PE3C4457	209	66
PE3C4458	210	73
PE3C4459	209	61
PE3C4460	210	74
PE3C4461	210	83
PE3C4462	210	86
PE3C4463	183	89
PE3C4464	196	39
PE3C4465	199	6
PE3C4466	133	95
PE3C4467	157	73
PE3C4468	210	77
PE3C4470	209	71
PE3C4471	183	92
PE3C4472	192	34
PE3C4473	196	41
PE3C4474	199	8
PE3C4476	133	97
PE3C4478	157	75
PE3C4480	210	79
PE3C4481	209	56
PE3C4482	209	68
PE3C4483	210	72
PE3C4484	183	88
PE3C4485	192	32
PE3C4486	199	5
PE3C4487	133	94
PE3C4488	133	98
PE3C4489	157	72
PE3C4490	210	76
PE3C4750	162	95
PE3C4801	208	47
PE3C4807	146	52
PE3C4844	124	73
PE3C4845	128	65
PE3C4846	128	62
PE3C4848	127	27
PE3C4849	129	89
PE3C4850	125	87
PE3C4851	125	84
PE3C4852	125	79
PE3C4853	125	92
PE3C4854	126	7
PE3C4855	129	74
PE3C4856	127	43
PE3C4857	126	13
PE3C4858	129	79
PE3C4859	127	49
PE3C4860	125	1
PE3C4861	128	71
PE3C4862	127	37
PE3C4863	126	23
PE3C4864	129	86
PE3C4865	128	59
PE3C4866	126	18
PE3C4867	129	81
PE3C4868	128	54
PE3C4869	126	20
PE3C4870	129	83
PE3C4871	128	56
PE3C4872	125	77
PE3C4873	128	68
PE3C4874	128	63
PE3C4875	127	31
PE3C4876	129	91
PE3C4877	125	90
PE3C4878	125	85
PE3C4879	125	83
PE3C4880	125	94
PE3C4881	126	11
PE3C4882	126	76
PE3C4883	127	47
PE3C4884	126	17
PE3C4885	129	80
PE3C4886	128	53
PE3C4887	126	5
PE3C4888	128	72
PE3C4889	127	41
PE3C4890	126	25
PE3C4891	129	87
PE3C4892	128	61
PE3C4893	126	19
PE3C4894	129	82
PE3C4895	128	55
PE3C4896	126	21
PE3C4897	129	84
PE3C4898	128	57
PE3C4899	124	72
PE3C4900	128	64
PE3C4901	127	26
PE3C4902	129	88
PE3C4903	125	86
PE3C4904	125	78
PE3C4905	125	91
PE3C4906	126	6
PE3C4907	129	73
PE3C4908	127	42
PE3C4909	126	12
PE3C4910	129	78
PE3C4911	127	48
PE3C4912	125	99
PE3C4913	128	70
PE3C4914	127	36
PE3C4915	126	22
PE3C4916	129	85
PE3C4917	128	58
PE3C4918	125	95
PE3C4919	128	69
PE3C4920	127	32
PE3C4921	124	76
PE3C4922	127	30
PE3C4923	127	89
PE3C4924	125	82
PE3C4925	127	46
PE3C4926	126	10
PE3C4927	128	52
PE3C4928	126	16
PE3C4929	127	40
PE3C4930	126	4
PE3C4931	127	35
PE3C4934	125	98
PE3C4935	124	74
PE3C4936	128	66
PE3C4937	127	28
PE3C4938	125	88
PE3C4939	125	80
PE3C4940	127	44
PE3C4941	126	8
PE3C4943	127	50
PE3C4944	127	38
PE3C4945	126	2
PE3C4948	127	33
PE3C4949	125	96
PE3C4950	124	75
PE3C4951	127	29
PE3C4952	129	90
PE3C4953	125	81
PE3C4954	125	93
PE3C4955	126	9
PE3C4956	127	45
PE3C4957	126	15
PE3C4958	128	51
PE3C4959	126	3
PE3C4960	127	39
PE3C4961	126	24
PE3C4962	128	60
PE3C4963	125	97
PE3C4964	127	34
PE3C4969	208	28
PE3C5030	164	40
PE3C5233	198	97
PE3C5241	174	22
PE3C5242	180	91
PE3C5244	191	92
PE3C5246	177	98
PE3C5247	198	75
PE3C5248	189	46
PE3C5249	211	18
PE3C5250	214	95
PE3C5251	216	29
PE3C5252	213	64
PE3C5253	216	26
PE3C5254	214	5
PE3C5255	149	34
PE3C5256	163	30
PE3C5257	154	94
PE3C5258	183	99
PE3C5259	185	35
PE3C5260	215	17
PE3C5261	192	37
PE3C5262	192	40
PE3C5263	193	43
PE3C5264	199	11
PE3C5265	199	12
PE3C5266	199	13
PE3C5267	158	83
PE3C5268	158	10
PE3C5269	159	13
PE3C5270	164	43
PE3C5271	164	46
PE3C5272	164	47
PE3C5273	156	46
PE3C5274	164	33
PE3C5275	157	59
PE3C5276	164	35
PE3C5277	157	66
PE3C5278	164	39
PE3C5279	161	88
PE3C5280	162	92
PE3C5281	161	90
PE3C5282	162	93
PE3C5283	162	99
PE3C5284	162	98
PE3C5285	151	6
PE3C5286	161	68
PE3C5287	160	36
PE3C5480	185	37
PE3C5491	140	6
PE3C5670	221	44
PE3C5833	117	94
PE3C5834-12	102	2
PE3C5835	104	6
PE3C5835-12	355	36
PE3C5835-24	355	37
PE3C5835-36	355	38
PE3C5835-48	355	39
PE3C5836	118	16
PE3C5837	102	13
PE3C5838-12	102	16
PE3C5839	102	17
PE3C5840	112	76
PE3C5841	109	23
PE3C5842	112	79
PE3C5843	102	4
PE3C5844	102	5
PE3C5845	102	6
PE3C5846	111	64
PE3C5847	109	18
PE3C5848	112	67
PE3C5849	112	69
PE3C5850	112	72
PE3C5851	112	73
PE3C5852	111	60
PE3C5853	113	13
PE3C5854	110	41
PE3C5855	120	63
PE3C5856	102	21
PE3C5857	102	25
PE3C5858	102	26
PE3C5859	115	39
PE3C5860	111	55
PE3C5861	121	3
PE3C5862-12	102	34
PE3C5863	102	37
PE3C5864	102	38
PE3C5865	114	37
PE3C5866	111	53
PE3C5867	121	1
PE3C5868	155	31
PE3C5869	165	69
PE3C5870	166	79
PE3C5871	114	38
PE3C5872	111	54
PE3C5873	121	2
PE3C5874	156	33
PE3C5875	166	76
PE3C5876	166	87
PE3C5877	166	84
PE3C5878	115	46
PE3C5879	111	58
PE3C5880	122	9
PE3C5881	102	35
PE3C5882	166	80
PE3C5883	102	39
PE3C5884	115	40
PE3C5885	111	56
PE3C5886	121	5
PE3C5887	156	48
PE3C5888	174	23
PE3C5889	115	43
PE3C5890	111	57
PE3C5891	122	7
PE3C5892	157	61
PE3C5893	189	36
PE3C5894	177	95
PE3C5895	189	47
PE3C5950	111	66
PE3C5980	187	86
PE3C5998	104	7
PE3C6172	111	61
PE3C6173	111	65
PE3C6174	113	96
PE3C6175	112	84
PE3C6176	113	91
PE3C6177	115	54
PE3C6178	112	85
PE3C6179	112	86
PE3C6180	113	92
PE3C6181	118	24
PE3C6182	120	64
PE3C6183	122	19
PE3C6184	113	5
PE3C6185	116	69
PE3C6186	113	6
PE3C6187	112	68
PE3C6188	119	47
PE3C6189	122	15
PE3C6190	121	90
PE3C6191	121	97
PE3C6192	120	78
PE3C6193	121	84
PE3C6194	121	6
PE3C6195	122	8
PE3C6196	123	35
PE3C6197	123	40
PE3C6198	122	27
PE3C6199	123	32
PE3C6200	153	56
PE3C6201	154	98
PE3C6202	149	41
PE3C6203	161	64
PE3C6204	161	71
PE3C6205	152	14
PE3C6206	160	43
PE3C6207	175	40
PE3C6208	189	51
PE3C6209	161	89
PE3C6210	177	6
PE3C6211	161	91
PE3C6212	157	62
PE3C6213	156	44
PE3C6214	164	34
PE3C6215	163	19
PE3C6216	164	36
PE3C6217	163	21
PE3C6218	112	70
PE3C6219	114	35
PE3C6220	114	31
PE3C6221	114	23
PE3C6222	116	82
PE3C6223	114	24
PE3C6224	123	46
PE3C6225	114	32
PE3C6226	114	36
PE3C6227	115	60
PE3C6228	114	97
PE3C6229	114	98
PE3C6230	114	14
PE3C6231	116	77
PE3C6232	114	15
PE3C6233	117	95
PE3C6234	112	71
PE3C6235	117	99
PE3C6236	113	9
PE3C6237	116	74
PE3C6238	113	10
PE3C6239	117	90
PE3C6240	117	1
PE3C6241	117	4
PE3C6242	117	85
PE3C6243	114	28
PE3C6244	123	53
PE3C6245	117	91
PE3C6246	115	41
PE3C6247	115	42
PE3C6248	115	44
PE3C6249	117	92
PE3C6250	115	45
PE3C6251	102	24
PE3C6252	123	43
PE3C6253	102	36
PE3C6254	102	33
PE3C6255	165	56
PE3C6256	159	25
PE3C6257	162	1
PE3C6258	102	40
PE3C6259	193	52
PE3C6260	124	57
PE3C6261	102	15
PE3C6262	117	93
PE3C6263	115	47
PE3C6264	118	7
PE3C6275	137	20
PE3C6331-12	103	73
PE3C6332	115	61
PE3C6333	103	76
PE3C6338	103	79
PE3C6339	118	5
PE3C6343	103	81
PE3C6344	103	93
PE3C6345	115	55
PE3C6346	116	70
PE3C6347	103	82
PE3C6348	103	85
PE3C6349	121	85
PE3C6350	103	87
PE3C6351	102	56
PE3C6352	102	59
PE3C6353	118	6
PE3C6354	102	61
PE3C6355	115	56
PE3C6356	116	71
PE3C6357	103	62
PE3C6358	103	65
PE3C6359	121	86
PE3C6360	103	67
PE3C6361	103	68
PE3C6362	152	16
PE3C6363	103	71
PE3C6365	102	9
PE3C6368	102	12
PE3C6369	102	20
PE3C6370	102	23
PE3C6371	102	32
PE3C6372	103	90
PE3C6373	152	17
PE3C6374	160	44
PE3C6375	103	70
PE3C6376	152	18
PE3C6378	160	45
PE3C6379	103	89
PE3C6380	103	69
PE3C6381	102	8
PE3C6382	102	11
PE3C6383	102	14
PE3C6384	102	19
PE3C6385	102	22
PE3C6386	102	31
PE3C6387	112	87
PE3C6437	102	54
PE3C6445	104	8
PE3C6484	105	22
PE3C6485	107	68
PE3C6486	104	9
PE3C6487	105	23
PE3C6488	107	69
PE3C6489	104	10
PE3C6490	104	11
PE3C6491	107	70
PE3C6492	107	71
PE3C6493	103	74
PE3C6498	103	80
PE3C6499	103	77
PE3C6500	114	16
PE3C6501	103	83
PE3C6502	120	67
PE3C6503	123	44
PE3C6504	102	60
PE3C6505	102	57
PE3C6506	114	17
PE3C6507	103	63
PE3C6508	120	69
PE3C6509	123	45
PE3C6510	103	84
PE3C6511	103	78
PE3C6512	103	75
PE3C6513	103	64
PE3C6514	102	58
PE3C6515	102	55
PE3C6516	113	88
PE3C6605	176	73
PE3C6631	168	36
PE3C6632	168	33
PE3C6633	168	35
PE3C6634	103	77
PE3C6635	107	64
PE3C6636	107	65
PE3C6637	107	66
PE3C6638	104	16
PE3C6639	104	21
PE3C6640	106	55
PE3C7615	150	63
PE3C7715	132	83
PE3C7720	124	70
PE3C7803	106	54
PE3C7819	102	44
PE3C7820	109	17
PE3C7821	109	22
PE3C7822	109	24
PE3C7823	111	59
PE3C7824	111	62
PE3C7825	111	63
PE3C7826	102	45
PE3C7827	115	49
PE3C7828	113	95
PE3C7829	113	1
PE3C7830	113	2
PE3C7831	115	52
PE3C7832	115	59
PE3C7833	116	65
PE3C7834	116	66
PE3C7835	102	47
PE3C7836	119	46
PE3C7837	120	62
PE3C7838	120	72
PE3C7839	122	13
PE3C7840	122	18
PE3C7841	122	22
PE3C7842	149	40
PE3C7843	152	13
PE3C7844	153	55
PE3C7845	154	97
PE3C7846	160	41
PE3C7847	160	63
PE3C7848	161	70
PE3C7849	102	50
PE3C7850	165	60
PE3C7851	165	61
PE3C7852	165	62
PE3C7853	165	65
PE3C7854	165	63
PE3C7855	165	64
PE3C7856	102	41
PE3C7857	105	25
PE3C7858	105	27
PE3C7859	105	29
PE3C7860	105	36
PE3C7861	105	37
PE3C7862	105	38
PE3C7863-12	102	52
PE3C7864	177	5
PE3C7865	178	57
PE3C7866	180	92
PE3C7867	189	50
PE3C7868	190	89
PE3C7869	191	95
PE3C7870	102	51
PE3C7871	166	75
PE3C7872	166	77
PE3C7873	166	78
PE3C7874	166	83
PE3C7875	166	85
PE3C7876	166	86
PE3C7891	212	40
PE3C7907	114	20
PE3C7914	193	51
PE3C7931	159	28
PE3C7947	103	95
PE3C7948	103	97
PE3C7949	105	26
PE3C7950	103	2
PE3C7951	109	20
PE3C7952	103	10
PE3C7953	113	89
PE3C7954	113	93
PE3C7955	113	98
PE3C7956	115	50
PE3C7957	115	57
PE3C7958	116	63
PE3C7959	103	16
PE3C7960	119	44
PE3C7961	120	60
PE3C7962	120	73
PE3C7963	122	11
PE3C7964	122	16
PE3C7965	122	23
PE3C7966-12	103	20
PE3C7967	152	11
PE3C7968	160	39
PE3C7969	153	53
PE3C7970	154	95
PE3C7971	103	23
PE3C7972	165	58
PE3C7973	103	25
PE3C7974	166	73
PE3C7975	166	81
PE3C7976	103	26
PE3C7977	177	3
PE3C7978	189	48
PE3C7979	103	96
PE3C7980	103	98
PE3C7981	105	28
PE3C7982	103	3
PE3C7983	109	21
PE3C7984	103	13
PE3C7985	113	90
PE3C7986	113	94
PE3C7987	113	99
PE3C7988	115	51
PE3C7989	115	58
PE3C7990	116	64
PE3C7991	103	17
PE3C7992	119	45
PE3C7993	120	61
PE3C7994	120	74
PE3C7995	122	12
PE3C7996	122	17
PE3C7997	122	24
PE3C7998	103	21
PE3C7999	152	12
PE3C8000	160	40
PE3C8001	153	54
PE3C8002	154	96
PE3C8003	103	24
PE3C8004	165	59
PE3C8005	165	68
PE3C8006	166	74
PE3C8007	166	82
PE3C8008	175	39
PE3C8009	177	4
PE3C8010	189	49
PE3C8015	133	2
PE3C8051	102	42
PE3C8056	105	39
PE3C8060	102	43
PE3C8064	106	44
PE3C8133	196	49
PE3C8133-3	359	92
PE3C8134	201	45
PE3C8134-3	359	93
PE3C8135	201	57
PE3C8135-3	359	94
PE3C8136	201	55
PE3C8136-3	359	95
PE3C8137	185	52
PE3C8137-3	359	96
PE3C8138	185	54
PE3C8138-3	359	97
PE3C8139	196	50
PE3C8139-3	359	98
PE3C8140	197	53
PE3C8140-3	359	99
PE3C8141	201	46
PE3C8141-3	359	1
PE3C8142	201	44
PE3C8142-3	359	2
PE3C8143	201	58
PE3C8143-3	359	3
PE3C8144	185	53
PE3C8144-3	359	4
PE3C8145	196	51
PE3C8145-3	359	5
PE3C8146	197	54
PE3C8214	103	4
PE3C8216	112	77
PE3C8222	112	74
PE3C8224	110	31
PE3C8225	110	33
PE3C8226	109	25
PE3C8227	110	29
PE3C8228	109	26
PE3C8229	103	6
PE3C8230	112	80
PE3C8231	110	39
PE3C8232	110	42
PE3C8233	110	35
PE3C8234	110	37
PE3C8235	103	8
PE3C8236	112	82
PE3C8237	111	49
PE3C8238	111	51
PE3C8239	110	44
PE3C8240	110	46
PE3C8241	103	11
PE3C8242

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE3C8741	219	96
PE3C8742	219	98
PE3C8743	218	88
PE3C8744	220	17
PE3C8745	220	13
PE3C8746	218	74
PE3C8747	220	18
PE3C8748	220	14
PE3C8749	218	75
PE3C8813	219	97
PE3C8814	219	99
PE3C8815	219	89
PE3C8816	220	19
PE3C8817	220	15
PE3C8818	218	76
PE3C8873	220	20
PE3C8874	220	16
PE3C8875	218	77
PE3CA1000	199	19
PE3CA1001	199	20
PE3CA1002	199	21
PE3CA1003	199	17
PE3CA1004	199	18
PE3CA1005	199	16
PE3CA1006	199	22
PE3CA1007	199	14
PE3CA1008	165	52
PE3CA1009	165	53
PE3CA1010	165	54
PE3CA1011	164	50
PE3CA1012	164	51
PE3CA1013	164	49
PE3CA1014	165	55
PE3CA1015	164	48
PE3CA1016	200	30
PE3CA1017	200	31
PE3CA1018	200	32
PE3CA1019	200	28
PE3CA1020	200	29
PE3CA1021	200	33
PE3CA1022	200	25
PE3CA1023	186	61
PE3CA1024	186	62
PE3CA1025	186	63
PE3CA1026	186	59
PE3CA1027	186	60
PE3CA1028	186	58
PE3CA1029	186	64
PE3CA1030	185	56
PE3CA1031	222	65
PE3CA1031-60cm	358	81
PE3CA1032	222	73
PE3CA1032-60cm	358	82
PE3CA1033	200	27
PE3CA1035	176	76
PE3CA1036	178	31
PE3CA1037	190	73
PE3CA1038	197	71
PE3CA1039	176	77
PE3CA1040	178	30
PE3CA1041	190	71
PE3CA1042	180	8
PE3CA1043	212	33
PE3CA1044	213	70
PE3CA1045	214	3
PE3CA1046	213	76
PE3CA1047	150	56
PE3CA1048	152	35
PE3CA1049	160	62
PE3CA1050	163	26
PE3CA1052	218	71
PE3CA1053	218	72
PE3CA1054	218	69
PE3CA1055	218	70
PE3CA1056	218	68
PE3CA1057	218	73
PE3CA1058	217	60
PE3CA1067	172	60
PE3CA1102	196	44
PE3CA1102-3	358	85
PE3CA1103	196	45
PE3CA1103-3	358	87
PE3CA1104	197	55
PE3CA1104-3	358	84
PE3CA1105	197	56
PE3CA1105-3	358	86
PE3CA1106	197	57
PE3CA1106-3	358	88
PE3CA1107	196	43
PE3CA1107-3	358	83
PE3CA1130	175	37
PE3CA2517	107	67
PE3CA2517-12	355	32
PE3CA2517-24	355	33
PE3CA2517-36	355	34
PE3CA2517-48	355	35
PE3M0001	99	5
PE3M0002	99	6
PE3M0003	99	7
PE3M0004	99	8
PE3M0005	99	9
PE3M0006	99	10
PE3M0007	99	11
PE3M0008	99	36
PE3M0009	99	37
PE3M0010	99	38
PE3M0011	99	42
PE3M0012	99	43
PE3M0013	99	44
PE3M0014	99	39
PE3M0015	99	40
PE3M0016	99	41
PE3M0017	99	45
PE3M0018	99	47
PE3M0019	99	49
PE3M0020	99	46
PE3M0021	99	48
PE3M0022	99	50
PE3M0023	100	86
PE3M0024	100	87
PE3M0025	100	89
PE3M0026	100	88
PE3M0027	100	90
PE3M0028	100	21
PE3M0029	99	12
PE3M0030	99	13
PE3M0031	99	14
PE3M0032	99	15
PE3M0033	99	16
PE3M0034	99	17
PE3M0035	99	18
PE3M0036	99	51
PE3M0037	99	52
PE3M0038	99	53
PE3M0039	99	57
PE3M0040	99	58
PE3M0041	99	59
PE3M0042	99	54
PE3M0043	99	55
PE3M0044	99	56
PE3M0045	99	60
PE3M0046	99	62
PE3M0047	99	64
PE3M0048	99	61
PE3M0049	99	63
PE3M0050	99	65
PE3M0051	100	91
PE3M0052	100	92
PE3M0053	100	94
PE3M0054	100	93
PE3M0055	100	95
PE3M0056	100	22
PE3M0057	99	29
PE3M0058	99	30
PE3M0059	99	31
PE3M0060	99	32
PE3M0061	99	33
PE3M0062	99	34
PE3M0063	99	35
PE3M0064	99	66
PE3M0065	99	67
PE3M0066	99	68
PE3M0067	99	72
PE3M0068	99	73
PE3M0069	100	74
PE3M0070	99	69
PE3M0071	99	70
PE3M0072	99	71
PE3M0073	100	75
PE3M0074	100	77
PE3M0075	100	79
PE3M0076	100	76
PE3M0077	100	78
PE3M0078	100	80
PE3M0079	100	15
PE3M0080	100	16
PE3M0081	100	18
PE3M0082	100	17
PE3M0083	100	19
PE3M0084	100	25
PE3M0085	99	19
PE3M0086	99	20
PE3M0087	99	21
PE3M0088	99	22
PE3M0089	99	23
PE3M0090	100	96
PE3M0091	100	97
PE3M0092	100	98
PE3M0093	100	1
PE3M0094	100	2
PE3M0095	100	4
PE3M0096	100	99
PE3M0097	100	3
PE3M0098	100	5
PE3M0099	100	23
PE3M0100	99	24
PE3M0101	99	25
PE3M0102	99	26
PE3M0103	99	27
PE3M0104	99	28
PE3M0105	100	6
PE3M0106	100	7
PE3M0107	100	8
PE3M0108	100	10
PE3M0109	100	11
PE3M0110	100	13
PE3M0111	100	9
PE3M0112	100	12
PE3M0113	100	14
PE3M0114	100	24
PE3M0115	99	1
PE3M0116	99	2
PE3M0117	99	3
PE3M0118	99	4
PE3M0119	100	81
PE3M0120	100	82
PE3M0121	100	84
PE3M0122	100	83
PE3M0123	100	85
PE3M0124	100	20
PE3M0125	100	47
PE3M0126	100	49
PE3M0127	100	50
PE3M0128	100	48
PE3M0129	100	51
PE3M0130	100	53
PE3M0131	100	52
PE3M0132	100	44
PE3M0133	100	46
PE3M0134	100	45
PE3M0135	100	69
PE3M0136	100	70
PE3M0137	100	67
PE3M0138	100	72
PE3M0139	100	76
PE3M0140	100	74
PE3M0141	100	61
PE3M0142	100	65
PE3M0143	100	63
PE3M0144	100	71
PE3M0145	100	68
PE3M0146	100	73
PE3M0147	100	77
PE3M0148	100	75
PE3M0149	100	62
PE3M0150	100	66
PE3M0151	100	64
PE3M0152	100	57
PE3M0153	100	58
PE3M0154	100	60
PE3M0155	100	59
PE3M0156	100	54
PE3M0157	100	56
PE3M0158	100	55
PE3M0159	101	19
PE3M0160	101	21
PE3M0161	101	20
PE3M0162	101	16
PE3M0163	101	18
PE3M0164	101	17
PE3M0165	101	30
PE3M0166	101	29
PE3M0167	101	26
PE3M0168	101	28
PE3M0169	101	27
PE3M0170	101	25
PE3M0171	101	22
PE3M0172	101	24
PE3M0173	101	23
PE3M0174	100	26
PE3M0175	100	28
PE3M0176	100	27
PE3M0177	100	31
PE3M0178	100	30
PE3M0179	100	29
PE3M0180	101	81
PE3M0181	101	83
PE3M0182	101	82
PE3M0183	101	84
PE3M0184	101	86
PE3M0185	101	85
PE3M0186	100	78
PE3M0187	100	80
PE3M0188	100	79
PE3M0189	101	98
PE3M0190	101	97
PE3M0191	101	99
PE3M0192	101	2
PE3M0193	101	1
PE3M0194	101	94
PE3M0195	101	96
PE3M0196	101	95
PE3M0197	101	90
PE3M0198	101	91
PE3M0199	101	93
PE3M0200	101	92
PE3M0201	101	87
PE3M0202	101	89
PE3M0203	101	88
PE3M0204	101	34
PE3M0205	101	36
PE3M0206	101	35
PE3M0207	101	31
PE3M0208	101	33
PE3M0209	101	32
PE3M0210	101	45
PE3M0211	101	44
PE3M0212	101	41
PE3M0213	101	43
PE3M0214	101	42
PE3M0215	101	40
PE3M0216	101	37
PE3M0217	101	39
PE3M0218	101	38
PE3M0219	100	32
PE3M0220	100	34
PE3M0221	100	33
PE3M0222	100	37
PE3M0223	100	36
PE3M0224	100	35
PE3M0225	101	6
PE3M0226	101	7
PE3M0227	101	8
PE3M0228	101	9
PE3M0229	101	3
PE3M0230	101	5
PE3M0231	101	4
PE3M0232	101	13
PE3M0233	101	14
PE3M0234	101	15
PE3M0235	101	10
PE3M0236	101	12
PE3M0237	101	11
PE3M0238	101	49
PE3M0239	101	50
PE3M0240	101	46
PE3M0241	101	48
PE3M0242	101	47
PE3M0243	101	54
PE3M0244	101	51
PE3M0245	101	53
PE3M0246	101	52
PE3M0247	100	38
PE3M0248	100	40
PE3M0249	100	39
PE3M0250	100	42
PE3M0251	100	41
PE3T0101	175	32
PE3T0101-24	357	75
PE3T0102	178	55
PE3T0102-24	357	73
PE3T0103	149	36
PE3T0103-24	357	71
PE3T0104	153	50
PE3T0104-24	357	70
PE3T0105	171	38
PE3T0105-24	357	72
PE3T0201	175	33
PE3T0201-24	357	76
PE3T0202	178	56
PE3T0202-24	357	74
PE3T0301	175	34
PE3T0301-24	358	79
PE3T0302	149	37
PE3T0302-24	358	77
PE3T0303	171	39
PE3T0303-24	358	78
PE3T0401	175	35
PE3T0401-24	358	80
PE3T0500	106	51
PE3T0500-24	356	48
PE3T0500-36	356	49
PE3T0500-48	356	48
PE3T0600	106	57
PE3T0600-24	356	49
PE3T0600-36	356	49
PE3T0600-48	356	49
PE3T0660	107	62
PE3T0670	107	63
PE3T0700	106	56
PE3T0700-24	356	50
PE3T0700-36	356	50
PE3T0700-48	356	50
PE3T0800	104	12
PE3T0800-24	356	51
PE3T0800-500CM	356	51
PE3T0800-36	356	51
PE3T0800-48	356	51
PE3T0900	104	20
PE3T0900-24	356	52
PE3T0900-36	356	52
PE3T0900-48	356	52
PE3T1000	104	19
PE3T1000-24	356	53
PE3T1000-36	356	53
PE3T1000-48	356	53
PE3T1100	130	3
PE3T1101	132	57
PE3T1102	149	33
PE3T1103	153	46
PE3T1200	222	67
PE3T1201	222	74
PE3T1202	221	36
PE3T1203	221	43
PE3T1204	222	66
PE3T1205	222	64
PE3T1206	221	45
PE3T1220	104	4
PE3T1220-6	356	54
PE3T1220-12	356	54
PE3T1221	104	5
PE3T1221-6	356	55
PE3T1221-12	356	55
PE3VNA1801	175	42
PE3VNA1802	178	58
PE3VNA1803	149	42
PE3VNA1804	153	59
PE3VNA1805	156	49
PE3VNA1806	157	64
PE3VNA2603	108	93
PE3VNA2604	108	99
PE3VNA2605	107	72
PE3VNA2606	107	83
PE3VNA2607	109	15
PE3VNA2610	109	14
PE3VNA4001	107	73
PE3VNA4001	107	73
PE3VNA4002	108	84
PE3VNA4002	108	84
PE3VNA4004	106	53
PE3VNA4004	106	53
PE3VNA4005	106	58
PE3VNA4005	106	58
PE3VNA4007	108	87
PE3VNA4008	108	88
PE3W0013	158	86
PE3W0020	162	96
PE3W0032	133	84
PE3W0037	214	2
PE3W0099	141	29
PE3W0109	150	46
PE3W0135	198	96
PE3W0140	148	91
PE3W0148	133	88
PE3W0169	193	47
PE3W0177	173	76
PE3W0245	196	48
PE3W0250	173	79
PE3W0288	219	3
PE3W0305	168	23
PE3W0314	140	94
PE3W0365	175	61
PE3W0393	130	20
PE3W0415	164	45
PE3W0416	182	56
PE3W0417	150	76
PE3W0430	151	2
PE3W0447	159	27
PE3W0504	173	73
PE3W0507	173	72
PE3W0572	211	19
PE3W0597	204	32
PE3W0676	153	47
PE3W0780	213	74
PE3W0808	212	50
PE3W0825	196	47
PE3W0832	171	36
PE3W0852	188	23
PE3W0906	181	26
PE3W0921	188	21
PE3W0934	197	64
PE3W1041	130	1
PE3W1114	188	18
PE3W1127	151	3
PE3W1283	182	76
PE3W1300	141	26
PE3W1357	130	2
PE3W1379	216	31
PE3W1570	141	19
PE3W1582	175	31
PE3W1626	171	37
PE3W1634	135	38
PE3W1739	192	26
PE3W1818	135	54
PE3W1959	211	11
PE3W1992	131	41
PE3W2012	155	29
PE3W2209	138	37
PE3W2215	158	9
PE3W2336	187	83
PE3W2356	158	87
PE3W2390	193	54
PE3W2458	176	68
PE3W2466	178	50
PE3W2547	155	20
PE3W2744	188	17
PE3W2882	188	16
PE3W2943	138	46
PE3W2965	198	95
PE3W2976	162	9
PE3W2993	177	17
PE3W2994	190	90
PE3W3014	182	58
PE3W3030	203	5
PE3W3032	194	2
PE3W3078	168	30
PE3W3154	146	47
PE3W3175	215	18
PE3W3271	120	75
PE3W3310	141	17
PE3W3353	174	28
PE3W3361	138	48
PE3W3365	163	27
PE3W3377	135	37
PE3W3391	139	72
PE3W3417	215	19
PE3W3496	124	71
PE3W3503	167	16
PE3W3530	118	21
PE3W3550	107	61
PE3W3751	177	18
PE3W3763	192	24
PE3W3777	208	27
PE3W3803	147	65
PE3W3859	194	1
PE3W3922	108	2
PE3W3981	195	10
PE3W3991	161	87
PE3W4028	211	13
PE3W4051	156	43
PE3W4152	204	37
PE3W4161	202	66
PE3W4200	204	38
PE3W4201	211	12
PE3W4229	157	57
PE3W4230	148	10
PE3W4293	215	16
PE3W4417	197	69
PE3W4423	163	20
PE3W4442	177	24
PE3W4458	183	93
PE3W4476	182	57
PE3W4513	204	31
PE3W4530	222	75
PE3W4619	167	98
PE3W4623	200	23
PE3W4625	200	24
PE3W4763	164	41
PE3W4802	208	29
PE3W4854	134	23
PE3W4971	178	51
PE3W4994	209	66
PE3W5056	207	24
PE3W5081	140	87
PE3W5106	192	23
PE3W5192	104	1
PE3W5224	185	43
PE3W5242	212	49
PE3W5274	182	75
PE3W5298	188	25
PE3W5361	182	6
PE3W5401	158	6
PE3W5425	215	20
PE3W5426	206	2
PE3W5453	162	4
PE3W5481	208	30
PE3W5483	144	82
PE3W5498	206	4
PE3W5518	210	80
PE3W5541	215	23
PE3W5557	200	42
PE3W5610	216	33
PE3W5630	164	38
PE3W5645	141	18
PE3W5651	158	7
PE3W5673	207	23
PE3W5692	207	26
PE3W5740	207	25
PE3W5752	216	25
PE3W5762	216	32
PE3W5881	133	87
PE3W5930	200	41
PE3W5962	197	72
PE3W6017	208	44
PE3W6018	208	42
PE3W6020	223	1
PE3W6055	196	34
PE3W6085	193	55
PE3W6095	159	26
PE3W6096	161	66
PE3W6234	207	21
PE3W6365	148	3
PE3W6405	164	37
PE3W6410	183	84
PE3W6417	157	60
PE3W6425	189	39
PE3W6441	161	69
PE3W6444	220	29
PE3W6468	141	16
PE3W6580	213	75
PE3W6649	134	25
PE3W6660	189	40
PE3W6662	166	88
PE3W6701	182	73
PE3W6709	214	4
PE3W6717	208	43
PE3W6862	133	86
PE3W6863	152	24
PE3W6905	203	4
PE3W6981	129	75
PE3W7044	207	8
PE3W7068	144	85
PE3W7181	185	36
PE3W7265	211	14
PE3W7334	197	74
PE3W7396	141	27
PE3W7480	134	24
PE3W7481	110	48
PE3W7489	162	5
PE3W7491	107	79
PE3W7532	145	23
PE3W7591	143	79
PE3W7602	221	55
PE3W7646	215	7
PE3W7647	215	9
PE3W7649	214	93
PE3W7653	143	80
PE3W7894	144	84
PE3W7895	105	24
PE3W7899	154	80
PE3W08014	106	49
PE3W08023	209	50
PE3W08060	109	12
PE3W08067	150	61
PE3W08103	135	53
PE3W08322	205	76
PE3W08323	207	5
PE3W08325	201	47
PE3W08326	207	18
PE3W08333	106	50
PE3W08340	130	25
PE3W08374	173	75
PE3W08402	183	90
PE3W08408	189	37
PE3W08467	151	7
PE3W08531	103	72
PE3W08540	141	28
PE3W08544	142	38
PE3W08574	106	60
PE3W08629	129	77
PE3W08640	166	89
PE3W09079	214	91
PE3W10030	215	24
PE3W10074	196	33
PE3W10097	129	92
PE3W10654	188	15
PE3W10767	215	21
PE3W11883	120	80
PE4000	277	69
PE4002	274	95
PE4003	272	11
PE4004	277	34
PE4005	273	45
PE4006	264	23
PE4007	273	36
PE4008	272	27
PE4009	274	91
PE4010	253	80
PE4011	263	82
PE4013	Web	
PE4014	253	71
PE4015	253	69
PE4016	251	14
PE4017	287	17
PE4018	251	99
PE4019	287	8
PE4020	293	23
PE4021	293	25
PE4022	290	5
PE4023	251	92
PE4024	251	93
PE4025	274	7
PE4026	272	3
PE4027	272	9
PE4028	274	82
PE4030	274	18
PE4031	274	19
PE4032	275	67
PE4033	275	68
PE4034	277	42
PE4035	273	46
PE4036	273	50
PE4037	274	10
PE4038	274	11
PE4039	275	40
PE4040	275	41
PE4041	264	33
PE4042	251	12
PE4044	282	28
PE4045	281	80
PE4046	289	63
PE4047	265	51
PE4048	253	74
PE4049	282	37
PE4051	281	91
PE4053	252	25
PE4054	289	94
PE4055	253	85
PE4056	253	76
PE4057	252	42
PE4058	252	41
PE4059	266	24
PE4060	268	95
PE4061	266	21
PE4062	264	28
PE4063	291	49
PE4064	291	53
PE4064SP	291	52
PE4065	291	47
PE4067	289	58
PE4068	290	11
PE4069	293	21
PE4070	252	43
PE4071	289	80
PE4072	266	22
PE4073	293	22
PE4074	282	29
PE4075	260	10
PE4076	260	3
PE4077	253	73
PE4078	252	57
PE4079	252	45
PE4080	281	81
PE4081	264	29
PE4082	251	21
PE4083	274	4
PE4084	251	90
PE4088	289	57
PE4089	304	65
PE4091	253	70
PE4092	252	33
PE4093	260	9
PE4094	283	44
PE4095	283	53
PE4096	281	99
PE4097	281	11
PE4098	260	4
PE4099	277	74
PE4100	271	81
PE4101	276	99
PE4104	303	60
PE4105	303	63
PE4106	252	59
PE4107	283	62
PE4108	274	83
PE4109	251	95
PE4110	301	7
PE4111	277	73
PE4112	273	43
PE4113	267	54
PE4114	267	60
PE4115	275	34
PE4116	275	37
PE4117	275	60
PE4118	Web	
PE4119	276	87
PE4120	Web	
PE4121	277	44
PE4123	278	90
PE4125	273	66
PE4126	274	77
PE4127	273	67
PE4128	277	38
PE4128-SF	277	39
PE4129	264	24
PE4130	266	17
PE4131	265	74
PE4132	264	31
PE4133	264	16
PE4134	266	25
PE4135	265	82
PE4136	265	81
PE4137	268	87
PE4138	266	16
PE4139	268	85
PE4140	265	59
PE4141	268	94
PE4142	289	54
PE4143	289	53
PE4144	290	7
PE4145	290	6
PE4146	289	92
PE4147	Web	
PE4148	291	40
PE4149	290	26
PE4150	290	25
PE4151	290	36
PE4152	290	29
PE4153	290	35
PE4154	289	59
PE4155	290	10
PE4156	289	79
PE4157	Web	
PE4158	301	18
PE4159	281	92
PE4160	282	38
PE4161	Web	
PE4162	301	22
PE4163	301	5
PE4164	302	27
PE4167	282	17
PE4168	301	10
PE4169	302	33
PE4170	282	18
PE4171	283	63
PE4172	301	9
PE4173	302	34
PE4174	281	8
PE4175	283	50
PE4176	302	28
PE4177	282	22
PE4178	283	66
PE4179	301	11
PE4180	302	35
PE4181	260	17
PE4182	258	35
PE4183	258	49
PE4184	285	63
PE4186	277	76
PE4188	276	90
PE4189	276	5
PE4190	275	63
PE4191	266	35
PE4192	259	58
PE4193	261	29
PE4194	273	86
PE4195	252	32
PE4196	276	10
PE4197	276	11
PE4198	258	36
PE4199	285	64
PE4200	281	78
PE4201	282	25
PE4202	282	26
PE4203	300	95
PE4204	252	36
PE4205	252	37
PE4206	251	88
PE4207	251	89
PE4208	253	64
PE4209	253	63
PE4210	251	6
PE4211	251	20
PE4212	252	40
PE4213	273	47
PE4214	272	4
PE4215	272	28
PE4217	277	66
PE4218	277	72
PE4219	Web	
PE4221	264	25
PE4222	Web	
PE4223	267	59
PE4224	264	27
PE4225	260	16
PE4226	260	13
PE4227	260	14
PE4228	261	37
PE4229	258	45
PE4229-401	258	46
PE4230	258	43
PE4231	271	75
PE4232	271	74
PE4233	258	32
PE4234	303	52
PE4235	303	54
PE4236	303	51
PE4237	303	53
PE4238	303	57
PE4239	272	93
PE4240	255	54
PE4241	255	61
PE4242	255	35
PE4243	255	32
PE4244	255	42
PE4245	281	96
PE4246	283	42
PE4247	251	5
PE4248	300	96
PE4249	301	19
PE4250	281	79
PE4251	300	2
PE4252	Web	
PE4254	302	26
PE4255	301	8
PE4256	302	31
PE4257	300	94
PE4258	301	17
PE4259	301	16
PE4260	281	89
PE4261

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE4387	252	24
PE4388	252	23
PE4389	252	39
PE4391	252	54
PE4392	252	61
PE4393	252	29
PE4394	253	79
PE4395	253	81
PE4396	252	30
PE4397	252	47
PE4398	272	25
PE4399	272	5
PE4400	272	6
PE4401	272	26
PE4402	273	48
PE4403	272	2
PE4404	273	39
PE4405	274	96
PE4406	274	8
PE4407	274	85
PE4408	274	93
PE4409	274	9
PE4411	274	17
PE4412	275	26
PE4413	275	27
PE4414	274	22
PE4415	274	16
PE4416	275	24
PE4417	275	39
PE4418	275	31
PE4419	275	75
PE4420	276	76
PE4421	275	65
PE4422	275	70
PE4423	276	88
PE4424	275	66
PE4425	275	72
PE4426	276	89
PE4427	275	74
PE4429	264	48
PE4430	265	50
PE4432	265	54
PE4433	264	26
PE4434	264	22
PE4435	266	34
PE4436	266	37
PE4437	266	20
PE4438	266	32
PE4439	266	15
PE4440	267	63
PE4441	267	56
PE4442	267	71
PE4443	267	55
PE4444	268	5
PE4445	255	39
PE4446	289	77
PE4447	289	78
PE4448	289	56
PE4449	289	49
PE4450	290	2
PE4451	290	95
PE4452	289	94
PE4453	Web	
PE4454	289	91
PE4455	290	99
PE4456	Web	
PE4457	290	16
PE4458	290	17
PE4459	290	18
PE4460	290	12
PE4461	290	8
PE4462	290	14
PE4463	290	9
PE4464	290	30
PE4465	290	37
PE4466	290	33
PE4467	290	28
PE4468	291	50
PE4469	291	45
PE4470	289	88
PE4471	291	57
PE4472	300	97
PE4473	258	38
PE4474	258	39
PE4475	258	33
PE4476	258	34
PE4477	258	40
PE4478	258	41
PE4479	258	37
PE4480	258	44
PE4481	258	47
PE4482	265	92
PE4483	Web	
PE4484	265	93
PE4485	265	94
PE4486	268	14
PE4487	268	9
PE4488	268	86
PE4489	265	71
PE4490	265	69
PE4490BK	265	70
PE4491	265	73
PE4492	268	9
PE4493	260	6
PE4494	260	1
PE4495	261	31
PE4496	271	83
PE4497	271	85
PE4498	271	79
PE4499	272	95
PE4500	272	94
PE4501	272	96
PE4502	299	80
PE4503	300	85
PE4504	299	79
PE4505	300	84
PE4506	300	83
PE4507	299	73
PE4508	299	78
PE4509	299	70
PE4510	299	75
PE4511	299	72
PE4512	299	77
PE4513	299	71
PE4514	299	82
PE4515	Web	
PE4516	299	81
PE4517	255	40
PE4518	255	37
PE4520	271	72
PE4521	262	53
PE4522	281	95
PE4523	281	84
PE4524	276	97
PE4525	273	61
PE4526	Web	
PE4527	277	71
PE4528	276	4
PE4529	276	1
PE4530	276	7
PE4531	273	63
PE4532	276	8
PE4533	277	75
PE4534	275	62
PE4536	276	3
PE4537	277	70
PE4538	277	68
PE4539	277	77
PE4540	277	67
PE4541	274	75
PE4542	275	55
PE4543	275	56
PE4544	Web	
PE4545	278	82
PE4547	276	9
PE4548	277	43
PE4549	276	2
PE4550	264	43
PE4551	259	67
PE4552	259	65
PE4553	259	73
PE4554	259	74
PE4555	260	89
PE4556	260	98
PE4558	282	27
PE4559	259	72
PE4560	260	99
PE4561	260	93
PE4562	260	81
PE4563	258	50
PE4564	258	51
PE4565	Web	
PE4567	247	72
PE4568	248	82
PE4569	248	83
PE4570	247	80
PE4571	247	81
PE4572	249	29
PE4573	249	34
PE4574	249	36
PE4574A	249	37
PE4575	248	15
PE4576	273	31
PE4577	273	32
PE4578	272	18
PE4579	274	84
PE4580	274	94
PE4587	273	54
PE4589	273	30
PE4590	273	53
PE4591	274	15
PE4592	275	38
PE4593	281	83
PE4595	281	94
PE4596	282	40
PE4597	Web	
PE4598	295	76
PE4599	295	55
PE4600	295	74
PE4601	295	57
PE4602	295	60
PE4603	295	56
PE4604	295	75
PE4605	296	81
PE4607	296	80
PE4608	296	83
PE4609	296	79
PE4610	296	82
PE4611	296	86
PE4613	296	85
PE4615	296	84
PE4616	296	88
PE4617	296	12
PE4618	296	14
PE4619	296	6
PE4620	296	4
PE4621	296	8
PE4622	296	18
PE4623	296	10
PE4624	296	7
PE4625	295	78
PE4626	296	5
PE4627	295	77
PE4628	296	19
PE4630	296	11
PE4631	296	13
PE4632	252	55
PE4633	295	70
PE4634	295	73
PE4635	Web	
PE4637	296	93
PE4638	296	99
PE4639	296	92
PE4640	296	98
PE4641	296	95
PE4642	296	97
PE4643	251	9
PE4644	262	62
PE4645	266	18
PE4646	266	16
PE4647	264	49
PE4648	289	84
PE4649	289	86
PE4650	251	18
PE4651	251	19
PE4652	266	41
PE4653	266	43
PE4654	267	78
PE4655	267	80
PE4656	299	76
PE4657	260	8
PE4658	301	20
PE4659	291	63
PE4660	292	71
PE4661	292	72
PE4662	291	64
PE4663	292	73
PE4664	292	74
PE4665	291	65
PE4666	292	75
PE4667	291	61
PE4668	292	69
PE4669	291	62
PE4670	291	59
PE4671	292	76
PE4672	291	60
PE4673	292	77
PE4674	291	58
PE4676	292	81
PE4677	292	84
PE4678	292	85
PE4679	292	82
PE4680	292	80
PE4681	292	83
PE4682	292	79
PE4683	292	89
PE4684	292	91
PE4685	292	97
PE4686	292	98
PE4687	292	99
PE4688	292	92
PE4689	292	90
PE4690	292	96
PE4691	292	88
PE4692	292	86
PE4693	292	87
PE4694	292	5
PE4695	293	11
PE4696	292	7
PE4698	Web	
PE4699	292	4
PE4700	292	6
PE4701	292	3
PE4702	292	1
PE4703	292	2
PE4704	293	13
PE4705	293	14
PE4706	293	12
PE4707	Web	
PE4708	292	78
PE4709	260	12
PE4710	260	11
PE4711	253	89
PE4712	253	93
PE4713	253	94
PE4714	253	90
PE4715	253	95
PE4716	254	96
PE4717	253	91
PE4718	254	97
PE4719	253	87
PE4720	253	92
PE4721	253	88
PE4722	253	86
PE4726	Web	
PE4727	254	1
PE4728	254	2
PE4729	254	4
PE4730	254	5
PE4731	Web	
PE4732	254	99
PE4733	254	3
PE4735	254	10
PE4736	254	11
PE4737	254	14
PE4738	254	15
PE4739	254	16
PE4740	Web	
PE4741	254	8
PE4742	254	12
PE4743	254	9
PE4744	254	6
PE4745	254	7
PE4746	254	19
PE4747	254	22
PE4748	254	23
PE4749	254	20
PE4751	254	18
PE4752	254	21
PE4755	254	17
PE4756	254	28
PE4757	254	25
PE4758	254	24
PE4759	254	29
PE4760	Web	
PE4762	254	98
PE4763	254	27
PE4764	254	26
PE4765	Web	
PE4766	278	93
PE4767	278	1
PE4768	278	6
PE4769	278	2
PE4770	278	91
PE4771	278	97
PE4772	278	4
PE4773	278	92
PE4774	Web	
PE4775	278	5
PE4777	278	94
PE4779	Web	
PE4780	278	8
PE4782	278	16
PE4784	278	7
PE4785	278	9
PE4786	278	15
PE4787	Web	
PE4788	278	10
PE4790	278	14
PE4791	Web	
PE4792	278	18
PE4793	279	24
PE4794	279	31
PE4795	279	25
PE4797	279	21
PE4798	279	29
PE4799	279	22
PE4800	256	67
PE4801	256	68
PE4804	256	71
PE4807	256	69
PE4808	256	62
PE4809	Web	
PE4812	256	64
PE4814	Web	
PE4815	256	63
PE4816	256	72
PE4838	256	70
PE4850	278	17
PE4851	279	30
PE4852	279	27
PE4853	279	28
PE4854	279	36
PE4855	279	41
PE4856	279	47
PE4857	279	42
PE4858	279	34
PE4859	279	37
PE4860	279	45
PE4861	279	35
PE4862	279	38
PE4863	279	46
PE4864	279	43
PE4865	279	44
PE4866	279	52
PE4867	279	51
PE4868	279	49
PE4869	279	33
PE4870	279	53
PE4871	279	50
PE4872	279	48
PE4873	Web	
PE4874	279	32
PE4875	280	54
PE4876	259	70
PE4877	259	78
PE4878	259	66
PE4879	259	75
PE4880	259	69
PE4881	259	68
PE4882	259	77
PE4883	259	76
PE4884	260	82
PE4885	260	83
PE4886	Web	
PE4887	260	91
PE4888	260	92
PE4889	260	88
PE4890	260	96
PE4891	260	95
PE4892	260	85
PE4893	260	84
PE4894	260	94
PE4896	263	80
PE4897	263	82
PE4898	263	88
PE4899	263	89
PE4901	263	93
PE4902	263	94
PE4903	263	1
PE4904	263	99
PE4905	263	87
PE4906	302	29
PE4907	273	42
PE4908	251	17
PE4909	289	82
PE4910	275	59
PE4911	277	80
PE4912	273	59
PE4913	273	60
PE4914	276	79
PE4915	252	51
PE4916	252	52
PE4917	273	38
PE4918	273	37
PE4919	274	99
PE4920	274	98
PE4921	275	30
PE4922	275	29
PE4923	276	81
PE4924	276	80
PE4926	281	1
PE4927	Web	
PE4928	301	3
PE4930	275	33
PE4931	276	83
PE4932	274	3
PE4933	260	5
PE4934	265	56
PE4935	265	80
PE4936	266	98
PE4937	266	1
PE4938	265	76
PE4940	267	73
PE4941	267	74
PE4942	267	53
PE4943	267	49
PE4945	266	38
PE4946	267	75
PE4949	255	46
PE4950	255	33
PE4951	255	30
PE4952	255	36
PE4953	255	31
PE4954	255	34
PE4955	255	45
PE4957	255	43
PE4958	255	47
PE4959	255	44
PE4960	255	49
PE4961	255	50
PE4962	Web	
PE4963	255	48
PE4964	255	51
PE4965	255	53
PE4967	255	58
PE4969	255	59
PE4970	Web	
PE4971	Web	
PE4972	255	55
PE4973	255	56
PE4974	251	16
PE4975	289	81
PE4978	271	77
PE4979	271	76
PE4980	271	78
PE4981	245	14
PE4982	245	15
PE4985	246	18
PE4987	244	49
PE4988	244	50
PE4989	Web	
PE4992	245	69
PE4993	299	61
PE4994	299	62
PE4995	299	63
PE4996	299	64
PE4997	299	66
PE4998	299	68
PE40001	295	69
PE40002	298	49
PE40003	294	40
PE40004	298	50
PE40005	294	41
PE40006	296	90
PE40007	296	16
PE40008	296	15
PE40009	296	1
PE40010	296	91
PE40011	296	17
PE40012	296	2
PE40013	298	53
PE40014	298	54
PE40015	298	52
PE40016	298	51
PE40017	294	47
PE40018	294	48
PE44000	277	46
PE44001	277	48
PE44003	277	50
PE44004	277	52
PE44005	273	68
PE44007	273	71
PE44008	273	72
PE44009	273	74
PE44010	277	47
PE44015	278	88
PE44018	273	69
PE44019	273	70
PE44020	Web	
PE44021	273	73
PE44022	Web	
PE44024	276	13
PE44025	Web	
PE44032	273	64
PE44033	Web	
PE44035	Web	
PE44036	256	66
PE44038	256	65
PE44040	Web	
PE44042	251	86
PE44045	264	15
PE44046	264	17
PE44047	283	56
PE44048	281	14
PE44049	272	90
PE44050	293	15
PE44051	293	19
PE44052	293	16
PE44053	293	20
PE44054	293	17
PE44055	293	26
PE44056	293	27
PE44057	293	28
PE44058	293	29
PE44059	293	30
PE44060	293	31
PE44061	289	48
PE44062	289	72
PE44065	268	97
PE44066	268	98
PE44068	268	1
PE44069	268	96
PE44070	268	93
PE44071	268	90
PE44072	268	91
PE44073	268	92
PE44074	268	10
PE44075	268	12
PE44076	268	11
PE44077	268	89
PE44079	268	88
PE44080	272	91
PE44083	262	56
PE44084	262	57
PE44085	262	55
PE44086	262	59
PE44087	262	58
PE44088	262	52
PE44089	262	61
PE44090	262	51
PE44091	262	63
PE44092	262	60
PE44093	Web	
PE44094	281	15
PE44095	283	57
PE44096	255	41
PE44098	Web	
PE44099	255	52
PE44100	261	19
PE44102	261	18
PE44103	261	20
PE44104	260	15
PE44105	261	22
PE44106	261	23
PE44107	261	25
PE44108	261	26
PE44109	261	24
PE44110	261	27
PE44111	261	21
PE44112	261	33
PE44114	303	56
PE44115	303	55
PE44116	303	59
PE44117	Web	
PE44118	271	88
PE44119	281	7
PE44120	283	49
PE44121	282	21
PE44122	283	65
PE44123	282	16
PE44124	283	61
PE44125	Web	
PE44127	Web	
PE44128	299	69
PE44129	281	5
PE44130	283	47
PE44131	299	65
PE44132	281	3
PE44133	Web	
PE44134	Web	
PE44135	281	6
PE44136	283	48
PE44137	281	4
PE44138	283	46
PE44139	282	19
PE44141	299	67
PE44142	282	20
PE44143	283	64
PE44145	304	67
PE44146	257	29
PE44147	257	28
PE44148	257	27
PE44149	257	26
PE44161	302	38
PE44162	302	42
PE44163	302	36
PE44164	302	39
PE44165	Web	
PE44166	302	41
PE44167	302	37
PE44168	Web	
PE44171	302	50
PE44172	302	49
PE44173	302	45
PE44174	302	43
PE44175	Web	
PE44176	302	44
PE44177	302	46
PE44178	302	48
PE44181	302	47
PE44182	280	58
PE44183	280	59
PE44184	280	55
PE44185	280	56
PE44186	280	62
PE44187	280	63
PE44188	280	60
PE44189	280	61
PE44190	280	66
PE44191	280	67
PE44192	280	64
PE44193	280	65
PE44194	280	73
PE44195	280	74
PE44196	280	71
PE44197	280	72
PE44198	280	70
PE44199	280	76
PE44200	280	75
PE44201	280	68
PE44202	280	69
PE44203	272	22
PE44204	275	51
PE44205	275	53
PE44206	275	50
PE44207	275	52
PE44208	275	54
PE44209	273	57
PE44210	273	58
PE44211	276	92
PE44212	276	94
PE44213	276	93
PE44214	276	95
PE44215	243	86
PE44216	243	91
PE44218	Web	
PE44220	243	88
PE44227	244	58
PE44229	245	70
PE44232	244	56
PE44235	275	58
PE44236	278	89
PE44237	278	84
PE44238	278	85
PE44239	278	86
PE44240	277	78
PE44241	277	79
PE44242	240	3
PE44243	240	4
PE44244	240	1
PE44247	240	8
PE44248	240	9
PE44249	240	6
PE44254	240	11
PE44255	Web	
PE44256	240	12
PE44257	240	10
PE44258	240	14
PE44259	240	13
PE44260	240	16
PE44261	240	15
PE44262	294	49
PE44263	294	50
PE44264	295	51
PE44265	Web	
PE44266	Web	
PE44267	Web	
PE44268	296	54
PE44270	295	52
PE44271	295	53
PE44274	285	50
PE44275	285	52
PE44276	247	70
PE44277	247	71
PE44278	247	69
PE44280	248	93
PE44282	248	92
PE44283	248	9
PE44284	248	14
PE44285	248	10
PE44286	248	16
PE44287	248	17
PE44288	248	8
PE44289	248	6
PE44290	248	7
PE44291	249	31
PE44292	249	30
PE44293	289	74
PE44294	251	8
PE44295	257	25
PE44296	257	24
PE44297	257	23
PE44298	298	55
PE44300	298	57
PE44303	260	90
PE44304	298	59
PE44307	Web	
PE44308	259	62
PE44309	259	59
PE44310	259	60
PE44311	259	63
PE44312	297	23
PE44313	297	29
PE44314	297	32
PE44315	297	26
PE44316	297	28
PE44317	297	22
PE44318	297	31
PE44320	297	35
PE44322	297	34
PE44323	297	36
PE44324	297	41
PE44325	Web	
PE44327	297	43
PE44329	297	44
PE44330	297	45
PE44331	297	37
PE44332	297	42
PE44333	297	46
PE44334	298	48
PE44336	241	24
PE44338	241	30
PE44340	277	33
PE44341	277	35
PE44345	Web	
PE44348	284	98
PE44349	264	18
PE44350	266	13
PE44351	241	55
PE44352	241	56
PE44353	241	53
PE44354	241	54
PE44355	242	58
PE44356	242	59
PE44357	242	71
PE44358	242	72
PE44359	242	66
PE44360	242	73
PE44361	242	63
PE44362	242	64
PE44363	242	61
PE44364	242	62
PE44365	242	69
PE44366	242	70
PE44367	242	67
PE44368	242	68
PE44369	263	2
PE44370	263	3
PE44373	Web	
PE44374	263	6
PE44376	264	8
PE44377	263	7
PE44378	286	67
PE44379	285	56
PE44380	286	68
PE44381	285	57
PE44382	286	69
PE44383	285	62
PE44384	286	72
PE44385	286	76
PE44386	286	77
PE44387	286	81
PE44388	286	85
PE44389	286	86
PE44390	286	90
PE44391	286	84
PE44392	286	97
PE44393	286	96
PE44394	287	6
PE44395	286	2
PE44396	267	48
PE44397	268	84
PE44398	268	13
PE44401	286	73
PE44402	286	74
PE44403	286	82
PE44404	286	83
PE44405	286	91
PE44406	286	92
PE44416	285	58
PE44418	286	69
PE44419	286	75
PE44420	286	70
PE44421	286	71
PE44422	286	78
PE44424	286	79
PE44425	286	80
PE44426	286	87
PE44427	286	93
PE44428	286	88
PE44429	286	89
PE44430	286	65
PE44431	Web	
PE44432	286	66
PE44433	286	1
PE44434	287	5
PE44435	287	7
PE44436	286	98
PE44437	286	99
PE44438	286	3
PE44439	286	4
PE44440	285	60
PE44441	285	61
PE44442	301	13
PE44443	301	12
PE44445	301	14
PE44446	301	15
PE44447	258	54
PE44448	258	53
PE44450	259	56
PE44451	259	55
PE44452	297	30
PE44453	263	5
PE44454	284	46
PE44455	287	11
PE44456	263	84
PE44457	263	91
PE44458	263	97
PE44459	263	96
PE44460	272	19
PE44461	272	23
PE44470	269	15
PE44472	269	16
PE44474	269	17
PE44475	269	20
PE44476	269	21
PE44477	269	19
PE44478	269	18
PE44480	284	82
PE44481	283	75
PE44482	283	71
PE44483	284	19
PE44484	Web	
PE44487	Web	
PE44489	261	40
PE44490	261	39
PE44491	261	44
PE44492	261	46
PE44493	261	48
PE44494	261	49
PE44495	270	36
PE44496	Web	
PE44497	270	46
PE44498	270	45
PE44500	270	56
PE44501	270	33
PE44503	270	32
PE44505	270	42
PE44506	270	40
PE44507	270	53
PE44508	270	54
PE44509	Web	
PE44510	270	51
PE44511	270	58
PE44512	270	52
PE44513	Web	
PE44514	270	34
PE44515	270	43
PE44520	264	32
PE44521	264	44
PE44522	264	45
PE44523	264	47
PE44524	265	86
PE44525	265	88
PE44526	265	89
PE44527	265	90
PE44528	267	69
PE44529	267	65
PE44530	267	66
PE44531	267	70
PE44532	266	28
PE44533	266	29
PE44534	266	30
PE44535	266	31
PE44536	247	79
PE44538	247	78
PE44541	248	96
PE44542	Web	
PE44543	Web	
PE44544	248	12
PE44545	248	11
PE44546	248	13
PE44548	249	23
PE44549	249	25
PE44550	249	24
PE44551	249	26
PE44554	265	75
PE44555	Web	
PE44558	247	68
PE44560	248	5
PE44561	Web	
PE44565	266	11
PE44568	247	66
PE44569	248	90
PE44572	297	20
PE44573	297	21
PE44574	300	87
PE44576	300	86
PE44577	295	59
PE44578	295	58
PE44579	297	33
PE44580	300	92
PE44582	297	25
PE44583	300	91
PE44584	295	71
PE44585	297	38
PE44586	300	93
PE44587	296	96
PE44588	299	60
PE44590	Web	
PE44591	276	6
PE44593	278	87
PE44594	294	34
PE44597	270	60
PE44599	270	63
PE44600	271	67
PE44601	271	65
PE44603	271	66
PE44604	271	68
PE44607	271	69
PE44608	271	70
PE44609	Web	
PE44610	271	71
PE44613	259	71
PE44614	275	57
PE44615	268	83
PE44616	252	50
PE44618	253	66
PE44619	296	89
PE44620	296	3
PE44622	300	90
PE44623	300	89
PE44624	300	88
PE44625	295	72
PE44626	295	61
PE44627	295	63
PE44628	295	66
PE44631	295	62
PE44632	295	64
PE44633	267

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE44646C	257	99
PE44646D	257	1
PE44646H	257	3
PE44646I	257	97
PE44646K	257	2
PE44646Z	257	4
PE44648A	257	9
PE44648B	257	15
PE44648C	257	10
PE44648D	257	11
PE44648H	257	13
PE44648I	257	8
PE44648K	257	12
PE44648Z	257	14
PE44649A	256	82
PE44649B	256	88
PE44649C	256	83
PE44649D	256	84
PE44649H	256	86
PE44649I	256	81
PE44649K	256	85
PE44649Z	256	87
PE44650A	257	17
PE44650B	257	22
PE44650C	257	18
PE44650D	257	19
PE44650H	257	20
PE44650I	257	16
PE44650K	Web	
PE44650Z	257	21
PE44651A	256	90
PE44651B	256	96
PE44651C	256	91
PE44651D	256	92
PE44651H	256	94
PE44651I	256	89
PE44651K	256	93
PE44651Z	256	95
PE44652	296	9
PE44653	265	72
PE44654	289	87
PE44655	285	41
PE44656	249	27
PE44658	252	60
PE44659	291	54
PE44660	260	87
PE44661	260	86
PE44662	263	98
PE44663	263	86
PE44664	278	95
PE44665	279	20
PE44666	278	96
PE44668	272	21
PE44669	274	21
PE44670	292	67
PE44671	292	94
PE44672	292	68
PE44673	292	95
PE44674	252	35
PE44675	265	61
PE44686	295	65
PE44687	296	94
PE44688	296	87
PE44690	273	44
PE44691	273	33
PE44692	274	6
PE44693	274	5
PE44694	275	36
PE44695	275	35
PE44696	276	86
PE44697	276	84
PE44698	259	79
PE44699	263	92
PE44700	265	62
PE44701	265	60
PE44702	266	99
PE44703	266	97
PE44704	266	42
PE44705	266	40
PE44706	267	79
PE44707	267	77
PE44708	289	85
PE44709	289	83
PE44710	290	4
PE44711	290	3
PE44712	290	21
PE44713	290	20
PE44714	291	41
PE44715	291	39
PE44717	249	33
PE44718	258	48
PE44719	294	32
PE44720	253	78
PE44721	268	2
PE44722	268	3
PE44723	279	26
PE44724	278	3
PE44726	264	11
PE44727	266	7
PE44728	247	65
PE44729	264	10
PE44731	266	6
PE44732	247	64
PE44734	248	4
PE44735	264	14
PE44737	266	10
PE44738	247	63
PE44740	248	3
PE44757	273	40
PE44775	284	83
PE44776	284	84
PE44777	283	72
PE44779	284	1
PE44780	284	2
PE44783	240	7
PE44784	263	90
PE44785	285	39
PE44786	285	40
PE44788	265	52
PE44789	266	36
PE44792	281	82
PE44796	244	43
PE44797	244	42
PE44798	244	57
PE44799	240	19
PE44800	241	31
PE44801	243	1
PE44802	241	38
PE44804	289	61
PE44807	267	52
PE44808	272	99
PE44809	264	21
PE44810	289	52
PE44811	290	23
PE44812	289	89
PE44813	267	50
PE44814	274	14
PE44815	289	50
PE44816	265	77
PE44817	274	78
PE44818	281	93
PE44825	264	19
PE44826	272	97
PE44827	275	61
PE44828	293	24
PE44830	259	80
PE44840	284	85
PE44842	287	14
PE44843	252	27
PE44844	265	87
PE44845	Web	
PE44846	290	97
PE44847	291	55
PE44848	283	59
PE44849	284	86
PE44852	263	95
PE44872	301	6
PE44874	263	83
PE44875	282	23
PE44876	282	39
PE44877	267	72
PE44879	283	73
PE44880	283	74
PE44886	252	56
PE44887	253	75
PE44888	253	77
PE44890	253	67
PE44891	253	68
PE44892	291	56
PE44893	Web	
PE44894	291	43
PE44895	298	47
PE44896	261	28
PE44897	290	22
PE44898	291	42
PE44899	290	31
PE44900	290	32
PE44901	291	51
PE44902	292	8
PE44903	292	9
PE44904	245	96
PE44905	245	95
PE44906	Web	
PE44907	284	22
PE44908	285	53
PE44909	285	30
PE44910	284	32
PE44911	285	51
PE44912	285	55
PE44913	285	56
PE44914	285	54
PE44915	285	49
PE44916	284	23
PE44917	285	38
PE44918	284	3
PE44919	284	4
PE44920	284	5
PE44921	284	6
PE44922	284	7
PE44923	284	8
PE44924	284	9
PE44925	284	10
PE44926	284	11
PE44927	284	12
PE44928	284	13
PE44930	284	14
PE44931	285	32
PE44932	284	99
PE44933	284	15
PE44934	285	36
PE44935	284	21
PE44936	284	88
PE44937	284	89
PE44938	284	28
PE44939	285	44
PE44940	284	90
PE44941	Web	
PE44942	283	69
PE44943	283	68
PE44944	284	76
PE44945	284	16
PE44946	284	77
PE44947	284	78
PE44948	284	24
PE44949	284	25
PE44950	284	26
PE44951	284	27
PE44952	284	79
PE44953	285	29
PE44954	Web	
PE44955	283	70
PE44956	285	33
PE44957	284	91
PE44958	284	92
PE44959	284	93
PE44960	284	94
PE44961	284	17
PE44962	Web	
PE44963	285	34
PE44964	285	35
PE44965	284	95
PE44966	284	96
PE44967	284	97
PE44968	261	42
PE44969	261	38
PE44970	261	41
PE44971	261	45
PE44972	261	50
PE44973	261	43
PE44974	261	47
PE44975	278	12
PE44976	264	9
PE44977	282	32
PE44978	270	61
PE44979	248	91
PE44993	247	67
PE44994	247	77
PE44996	274	81
PE44998	277	45
PE45000	249	35
PE45001	247	76
PE45002	265	61
PE45004	279	40
PE45005	240	20
PE45008	278	98
PE45011	246	16
PE45012	278	13
PE45032	242	60
PE45035	261	36
PE45036	266	8
PE45037	247	73
PE45039	277	36
PE45040	272	14
PE45041	274	80
PE45042	272	1
PE45045	251	97
PE45046	248	95
PE45047	267	67
PE45048	274	86
PE45050	263	5
PE45051	263	4
PE45053	277	53
PE45054	Web	
PE45055	276	14
PE45064	252	58
PE45065	289	75
PE45067	277	37
PE45071	270	62
PE45085	268	7
PE45086	298	56
PE45114	251	98
PE45116	295	68
PE45117	295	67
PE45119	281	85
PE45126	284	18
PE45127	284	20
PE45128	285	46
PE45130	291	46
PE45131	252	62
PE45132	291	38
PE45133	268	99
PE45134	276	96
PE45136	273	49
PE45136	275	73
PE45137	275	25
PE45138	276	77
PE45139	273	65
PE45140	272	10
PE45141	276	78
PE45142	272	8
PE45143	290	15
PE45144	274	94
PE45145	272	24
PE45147	283	60
PE45150	282	40
PE45153	287	18
PE45155	282	30
PE45156	283	45
PE45157	283	55
PE45158	281	2
PE45159	281	13
PE45161	289	62
PE45162	287	21
PE45164	304	64
PE45165	280	57
PE45166	240	2
PE45168	259	64
PE45169	259	61
PE45170	241	57
PE45171	242	65
PE45172	266	33
PE45173	267	58
PE45174	290	1
PE45176	257	6
PE45176Z	257	7
PE45177	290	34
PE45180	292	70
PE45181	293	10
PE45182	254	13
PE45183	278	99
PE45185	278	11
PE45186	279	23
PE45189	279	39
PE45193	282	41
PE45195	287	20
PE45203	266	9
PE45204	274	76
PE45205	302	32
PE45209	287	26
PE45210	283	58
PE45211	298	58
PE45215	277	51
PE45216	277	49
PE45217	276	17
PE45218	270	57
PE45222	270	59
PE45223	271	64
PE45224	270	31
PE45225	265	79
PE45227	294	36
PE45228	294	35
PE45229	294	45
PE45230	294	42
PE45231	294	46
PE45232	294	44
PE45233	294	37
PE45234	294	38
PE45235	294	39
PE45237	294	43
PE45239	252	34
PE45245	266	14
PE45248	285	48
PE45249	285	47
PE45250	262	64
PE45251	262	65
PE45252	262	66
PE45253	262	67
PE45254	262	70
PE45255	262	71
PE45256	262	72
PE45257	262	73
PE45261	262	74
PE45267	262	79
PE45274	260	97
PE45277	285	37
PE45282	274	1
PE45283	291	66
PE45284	270	41
PE45285	285	43
PE45287	285	42
PE45290	285	45
PE45292	275	71
PE45295	246	29
PE45296	246	30
PE45297	246	37
PE45298	246	38
PE45299	246	35
PE45300	246	36
PE45301	246	42
PE45302	247	48
PE45303	247	50
PE45304	247	61
PE45306	247	62
PE45307	258	42
PE45310	249	46
PE45311	249	47
PE45313	249	44
PE45314	249	45
PE45315	249	41
PE45316	249	43
PE45317	249	42
PE45318	249	40
PE45319	250	64
PE45320	250	63
PE45321	250	72
PE45322	250	73
PE45323	250	71
PE45324	250	66
PE45325	250	67
PE45326	250	74
PE45327	250	75
PE45328	250	65
PE45329	251	80
PE45330	251	81
PE45331	251	82
PE45332	251	79
PE45333	250	61
PE45334	250	77
PE45335	249	38
PE45336	249	39
PE45337	250	69
PE45338	250	68
PE45339	250	56
PE45340	250	76
PE45341	249	51
PE45342	249	52
PE45343	249	53
PE45344	249	54
PE45345	249	48
PE45346	249	49
PE45347	249	55
PE45348	249	50
PE45349	250	57
PE45350	250	58
PE45351	250	59
PE45352	250	60
PE45353	250	78
PE45354	250	62
PE45355	Web	
PE45358	287	23
PE45365	287	22
PE45366	288	35
PE45370	288	34
PE45371	288	38
PE45375	288	33
PE45376	288	42
PE45377	288	47
PE45378	288	32
PE45379	288	40
PE45380	288	31
PE45384	288	30
PE45385	288	43
PE45387	288	45
PE45388	288	46
PE45389	288	39
PE45390	288	41
PE45391	288	46
PE45395	252	46
PE45396	282	31
PE45397	279	19
PE45398	246	17
PE45398	354	21
PE45400	244	61
PE45401	243	92
PE45402	241	34
PE45403	240	18
PE45404A	256	74
PE45404B	256	80
PE45404C	256	75
PE45404D	256	76
PE45404H	256	78
PE45404I	256	77
PE45404K	256	77
PE45404Z	256	79
PE45405	286	94
PE45406	286	95
PE45410	241	21
PE45411	243	85
PE45412	244	44
PE45413	241	25
PE45414	243	87
PE45415	244	51
PE45417	247	55
PE45418	247	44
PE45419	247	51
PE45420	246	26
PE45421	246	20
PE45422	246	23
PE45423	248	20
PE45424	248	85
PE45425	248	95
PE45426	267	45
PE45427	265	64
PE45428	266	3
PE45429	270	50
PE45430	270	37
PE45431	270	47
PE45432	275	42
PE45434	274	12
PE45437	289	60
PE45440	272	98
PE45441	275	64
PE45442	274	79
PE45443	289	51
PE45444	290	24
PE45445	289	90
PE45446	264	20
PE45447	267	51
PE45448	265	78
PE45450	244	59
PE45451	244	60
PE45452	244	52
PE45453	244	53
PE45454	243	89
PE45455	243	90
PE45456	243	81
PE45457	243	82
PE45458	275	43
PE45459	275	44
PE45460	273	55
PE45461	273	56
PE45462	275	45
PE45463	275	46
PE45464	275	47
PE45465	275	48
PE45466	275	49
PE45467	244	62
PE45468	244	63
PE45469	244	64
PE45470	244	65
PE45471	244	66
PE45472	243	93
PE45473	243	94
PE45474	243	95
PE45475	243	96
PE45476	243	97
PE45477	241	35
PE45478	294	33
PE45479	271	73
PE45480	273	35
PE45481	273	34
PE45482	241	22
PE45483	244	47
PE45484	241	23
PE45485	244	48
PE45486	244	45
PE45487	244	46
PE45490	287	25
PE45491	287	24
PE45492	Web	
PE45493	288	36
PE45494	288	37
PE45496	288	27
PE45497	288	28
PE45498	288	29
PE45499	288	44
PE45502	267	47
PE45502	354	22
PE45504	297	39
PE45505	265	68
PE45506	354	67
PE45507	244	67
PE45508	244	68
PE45509	244	54
PE45510	244	55
PE45511	243	98
PE45512	243	99
PE45513	243	83
PE45514	243	84
PE45515	241	36
PE45516	241	37
PE45517	241	28
PE45518	241	29
PE45519	259	57
PE45520	297	27
PE45527	289	76
PE45543	273	51
PE45546	274	89
PE45547	276	98
PE45552	297	40
PE45554	276	85
PE45556	272	89
PE45560	277	54
PE45561	277	56
PE45562	277	58
PE45563	277	60
PE45564	277	62
PE45565	277	64
PE45566	277	55
PE45567	277	57
PE45568	277	59
PE45569	277	61
PE45570	277	63
PE45571	277	65
PE45572	276	15
PE45573	276	18
PE45574	276	21
PE45575	276	24
PE45576	276	27
PE45577	276	30
PE45578	276	16
PE45579	276	19
PE45580	276	22
PE45581	276	25
PE45582	276	28
PE45583	276	31
PE45584	276	17
PE45585	276	20
PE45586	276	23
PE45587	276	26
PE45588	276	29
PE45589	276	32
PE45590	245	97
PE45591	245	99
PE45592	245	2
PE45593	245	4
PE45594	245	98
PE45595	245	1
PE45596	245	3
PE45597	245	5
PE45598	245	73
PE45599	245	76
PE45600	245	79
PE45601	245	82
PE45602	245	71
PE45603	245	74
PE45604	245	77
PE45605	245	80
PE45606	245	72
PE45607	245	75
PE45608	245	78
PE45609	245	81
PE45610	244	27
PE45611	244	29
PE45612	244	31
PE45613	244	33
PE45614	244	26
PE45615	244	28
PE45616	244	30
PE45617	244	32
PE45618	243	4
PE45619	243	7
PE45620	243	10
PE45621	243	13
PE45622	243	2
PE45623	243	5
PE45624	243	8
PE45625	243	11
PE45626	243	3
PE45627	243	6
PE45628	243	9
PE45629	243	12
PE45630	241	48
PE45631	241	47
PE45632	241	39
PE45633	241	40
PE45639	290	19
PE45640	248	97
PE45650	246	19
PE45651	246	22
PE45652	246	25
PE45653	246	28
PE45654	246	39
PE45655	247	49
PE45656	247	54
PE45657	247	58
PE45658	246	40
PE45659	246	41
PE45660	248	84
PE45661	248	98
PE45662	248	18
PE45663	249	28
PE45664	265	57
PE45665	266	96
PE45666	266	39
PE45667	267	76
PE45668	269	22
PE45669	269	25
PE45670	269	27
PE45671	269	28
PE45672	269	23
PE45673	242	74
PE45674	242	77
PE45675	242	78
PE45676	242	80
PE45677	242	75
PE45678	273	41
PE45679	274	2
PE45680	275	32
PE45681	276	82
PE45682	270	35
PE45683	270	44
PE45684	270	49
PE45685	270	55
PE45686	247	60
PE45687	302	40
PE45688	241	32
PE45689	241	33
PE45690	241	26
PE45691	241	27
PE45692	240	17
PE45698	277	81
PE45702	245	6
PE45703	245	8
PE45704	245	7
PE45705	245	9
PE45706	245	83
PE45707	245	87
PE45708	244	34
PE45709	244	36
PE45710	244	35
PE45711	244	37
PE45712	243	14
PE45713	243	17
PE45714	241	49
PE45715	241	50
PE45716	241	41
PE45717	245	10
PE45718	245	12
PE45719	245	11
PE45720	245	13
PE45721	245	90
PE45722	245	93
PE45723	244	38
PE45724	244	40
PE45725	244	39
PE45726	244	41
PE45727	243	20
PE45728	243	23
PE45729	241	51
PE45730	241	52
PE45731	241	43
PE45732	245	84
PE45733	245	91
PE45734	245	88
PE45735	245	94
PE45736	245	85
PE45737	245	92
PE45738	245	89
PE45739	245	86
PE45740	243	15
PE45741	243	21
PE45742	243	18
PE45743	243	24
PE45744	243	16
PE45745	243	22
PE45746	243	19
PE45747	243	25
PE45748	241	46
PE45749	241	44
PE45750	241	42
PE45751	241	45
PE4CO1013	255	57
PE45259TR1	262	68
PE45259TR750	262	69
PE45262TR1	262	75
PE45262TR750	262	76
PE45265TR1	262	77
PE45265TR500	262	78
PE45278TR1	284	80
PE45278TR1500		81
PE5004-KIT	361	31
PE5007	361	30
PE5008	361	32
PE5009	361	33
PE5010-1	361	35
PE5010-3	361	35
PE5011-3	360	6
PE5011-7	360	10
PE5011-6	360	14
PE5011-1	360	17
PE5011-2	360	18
PE5011-5	360	21
PE5011-8	360	28
PE5011-4	360	29
PE5012	361	34
PE5013	Web	
PE5019-16	360	1
PE5019-1A	360	2
PE5019-21	360	5
PE5019-6	360	7
PE5019-3	360	8
PE5019-5	360	9
PE5019-4	360	11
PE5019-7	360	12
PE5019-8	360	13
PE5019-19A	360	16
PE5019-11	360	19
PE5019-14	360	20
PE5019-13	360	22
PE5019-12	360	23
PE5019-18	360	24
PE5019-17	360	25
PE5019-9	360	26
PE5019-10	360	27
PE5020	360	3
PE5021	360	4
PE5022	360	15
PE5200	Web	
PE5201	Web	
PE5202	Web	
PE5500-1	Web	
PE5500-2	Web	
PE5500-3	Web	
PE5500-4	Web	
PE5500-5	Web	
PE5500-6	Web	
PE5511	Web	
PE51001	Web	
PE51021	269	29
PE51023	62	19
PE51024	62	8
PE51025	62	7
PE51026	69	24
PE51027	66	26
PE51028	65	98
PE51034	65	5
PE51040	65	8
PE51049	Web	
PE51050	Web	
PE51052	Web	
PE51054	62	5
PE51055	69	23
PE51056	69	22
PE51057	Web	
PE51058	65	96
PE51059	65	95
PE51060	Web	
PE51061	65	3
PE51062	65	99
PE51063	65	1
PE51064	65	4
PE51065	65	6
PE51066-1	66	15
PE51066-2	66	16
PE51067	66	11
PE51068	66	14
PE51072	Web	
PE51076	Web	
PE51077	69	31
PE51078	69	32
PE51080	69	35
PE51081	69	38
PE51082	69	36
PE51083	69	37
PE51084	69	44
PE51085	69	45
PE51087	69	33
PE51088	69	34
PE51089-1	69	18
PE51089-2	69	19
PE51089-3	69	20
PE51089-4	69	21
PE51090	Web	
PE51092	62	26
PE51098	65	97
PE51098-1	65	91
PE51098-2	65	92
PE51098-3	65	93
PE51098-4	65	94
PE51113-1	66	19
PE51113-2	66	20
PE51113-3	66	21
PE51113-4	66	22
PE51117A	69	26
PE51119	69	25
PE51120	Web	
PE51121	69	28
PE51122	Web	
PE51123	69	29
PE51124	Web	
PE51125A	69	48
PE51126	Web	
PE51127	69	49
PE51128	Web	
PE51129	63	27
PE51133	69	30
PE51134	69	47
PE51135A	69	46
PE51136	66	30
PE51142	69	39
PE51143	69	40
PE51144	69	41
PE51145	Web	
PE51146	68	97
PE51147	Web	
PE51148	Web	
PE51149	Web	
PE51150	Web	
PE51151	Web	
PE51152	68	11
PE51153	Web	
PE51154	68	10
PE51155	Web	
PE51156	Web	
PE51157	68	9
PE51158	65	90
PE51159	68	17
PE51160	68	99
PE51161	68	1
PE51162	Web	
PE51163	Web	
PE51164	69	16
PE51165	69	17
PE51166	69	14
PE51167	269	30
PE51168	Web	
PE51171	Web	
PE51172	65	2
PE51173	69	27
PE51194	68	79
PE51195	68	76
PE51196	68	80
PE51197	68	78
PE51198	68	77
PE51199	68	75
PE51200	67	74
PE51201	68	91
PE51202	68	92
PE51203	68	90
PE51204	68	84
PE51205	68	87
PE51206	68	83
PE51207	68	88
PE51208	68	85
PE51209	68	86
PE51210	68	89
PE51211	68	95
PE51212	66	9
PE51213	68	82
PE51214	68	93
PE51215	68	94
PE51216	68	81
PE51217	64	78
PE51218	64	80
PE51219	65	82
PE51220	65	84
PE51221	65	86
PE51222	65	88
PE51223	64	79
PE51224	64	81
PE51225	65	83
PE51226	65	85
PE51227	65	87
PE51228	62	89
PE51239	62	3
PE51240	253	83
PE51AK1000	71	87
PE51AK1001	71	88
PE51AK1002	71	89
PE51AK1003	71	90
PE51AK1004	71	91
PE51FP1001	62	23
PE51FP1002	62	22
PE51FP1003	62	20
PE51FP1004	62	21
PE51FP1005	62	14
PE51FP1005-1	62	15
PE51FP1005-2	62	16
PE51FP1005-3	62	17
PE51FP1005-4	62	18
PE51FP1006	62	6
PE51FP1007	62	9
PE51FP1008	62	10
PE51FP1008-1	62	11
PE51FP1008-2	62	12
PE51FP1008-3	62	13
PE51FP1009	64	72
PE51FP1010	62	24
PE51FP1011	62	25
PE51FP1012	62	1
PE51FP1013	62	2
PE51FP1014	62	4
PE51FP1015	67	72
PE51FP1016	67	73
PE51GM1001	71	86
PE51GM1002	66	18
PE51GPS1000	71	95
PE51GPS1001	71	92
PE51GPS1002	71	93
PE51GPS1003

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE51OM1013	67	42
PE51OM1014	67	41
PE51OM1015	67	43
PE51OM1016	67	44
PE51OM1017	67	46
PE51OM1018	67	47
PE51OM1019	67	45
PE51OM1020	66	37
PE51OM1021	69	15
PE51OM1022	66	25
PE51OM1023	66	28
PE51OM1024	67	51
PE51OM1025	67	53
PE51OM1026	67	54
PE51OM1027	68	3
PE51OM1028	68	7
PE51OM1029	68	4
PE51OM1030	68	2
PE51OM1031	67	39
PE51OM1032	67	40
PE51OM1033	66	33
PE51OM1034	66	35
PE51OM1035	66	35
PE51OM1036	66	36
PE51OM1038	66	38
PE51OM1039	66	31
PE51OM1040	66	32
PE51OM1041	67	49
PE51OM1042	67	50
PE51OM1043	67	48
PE51OM1044	67	67
PE51OM1045	67	52
PE51OM1046	67	68
PE51OM1047	67	71
PE51OM1048	67	70
PE51OM1049	67	69
PE51PD1001	63	52
PE51PD1002	63	51
PE51PD1003	63	50
PE51PD1004	63	47
PE51PD1005	63	48
PE51PD1006	63	49
PE51RD1001	70	68
PE51RD1002	70	69
PE51RD1003	70	70
PE51RD1004	70	71
PE51RD1005	70	73
PE51RD1006	70	72
PE51RD1007	70	66
PE51RD1008	70	50
PE51RD1009	70	51
PE51RD1010	70	53
PE51RD1011	70	54
PE51RD1012	70	55
PE51RD1013	70	60
PE51RD1014	70	63
PE51RD1015	70	64
PE51RD1016	70	65
PE51RD1017	70	67
PE51RD1018	70	56
PE51RD1019	70	52
PE51RD1020	70	57
PE51RD1021	70	59
PE51RD1022	70	58
PE51RD1023	70	61
PE51RD1024	70	62
PE51RD1025	69	42
PE51RD1026	69	43
PE51RD1027	69	12
PE51RD1028	69	13
PE51RD1030	68	6
PE51RD1031	68	5
PE51RD1032	68	8
PE51SE1001	64	74
PE51SE1002	64	75
PE51SE1003	64	71
PE51SE1004	64	70
PE51SE1005	64	69
PE51SE1006	64	68
PE51SE1007	64	76
PE51SE1008	64	77
PE51SE1009	64	73
PE51TM1000	66	12
PE51TM1001	66	13
PE51TW1000	68	96
PE51YA1001	63	42
PE51YA1002	63	43
PE51YA1003	63	44
PE51YA1004	63	41
PE51YA1005	63	46
PE51YA1006	63	45
PE51YA1007	63	29
PE51YA1008	63	30
PE51YA1009	63	31
PE51YA1010	63	32
PE51YA1011	63	33
PE51YA1012	63	38
PE51YA1013	63	39
PE51YA1014	63	40
PE51YA1015	63	28
PE51YA1016	63	35
PE51YA1017	63	34
PE51YA1018	63	37
PE51YA1019	63	36
PE5CK1000	353	7
PE5CK1001	353	5
PE5CK1002	353	17
PE5CK1012	354	19
PE5CK1013	354	20
PE5CK1015	353	1
PE5CK1016	353	2
PE5CK1017	353	3
PE5CK1018	353	4
PE5CK1019	353	8
PE5CK1020	353	9
PE5CK1021	353	10
PE5CK1022	353	11
PE5CK1023	353	12
PE5CK1024	353	13
PE5CK1025	353	15
PE5CK1026	353	16
PE5CK1027	Web	
PE5SC1000	Web	
PE5SC1001	Web	
PE5SC1002	Web	
PE5SC1003	Web	
PE5SC1004	Web	
PE5SC1005	Web	

Model No.	Page	C/R
PE5SC2000	Web	
PE5SC2001	Web	
PE5SC2002	Web	
PE5SC2003	Web	
PE5SC2004	Web	
PE5SC2005	Web	
PE5SC3000	Web	
PE5SC3001	Web	
PE5SC3002	Web	
PE5SC3003	Web	
PE5SC3004	Web	
PE5SC3005	Web	
PE5SC3010	Web	
PE5SC3011	Web	
PE5SC3012	Web	
PE5SC3013	Web	
PE5SC3014	Web	
PE5SC3015	Web	
PE5SC3016	Web	
PE5SC3017	Web	
PE5SC3018	Web	
PE5SC3019	Web	
PE5SC3020	Web	
PE5SC3023	Web	
PE5SC3024	Web	
PE5SC3025	Web	
PE5SC3026	Web	
PE5SC3027	Web	
PE5SC3028	Web	
PE5SC3029	Web	
PE5SC3030	Web	
PE5SC3031	Web	
PE5SC3032	Web	
PE5SC3033	Web	
PE5SC3034	Web	
PE5SC3035	Web	
PE5SC3038	Web	
PE5SC3039	Web	
PE5TL1000	354	32
PE5TR1000	Web	
PE5TR1001	Web	
PE5TR1002	Web	
PE5TR1003	Web	
PE5TR1004	Web	
PE5TR1005	Web	
PE5TR1006	Web	
PE5TR1007	Web	
PE5TR1008	Web	
PE5TR1009	Web	
PE5TR1010	Web	
PE5TR1011	Web	
PE5TR1012	Web	
PE5TR1013	Web	
PE5TR1014	Web	
PE5TR1015	Web	
PE5TR1016	Web	
PE5TR1019	Web	
PE5TR1020	Web	
PE6002	347	10
PE6006	306	48
PE6007	306	51
PE6009	349	93
PE6012	306	40
PE6013	305	4
PE6014	305	5
PE6015	305	6
PE6016	306	17
PE6017	306	18
PE6018	306	19
PE6019	306	23
PE6020	306	32
PE6021	306	35
PE6022	306	44
PE6023	306	33
PE6024	306	24
PE6026	351	25
PE6030	306	42
PE6031	306	46
PE6032	349	96
PE6033	351	24
PE6034	349	32
PE6035	349	35
PE6036	349	37
PE6037	350	52
PE6038	350	55
PE6039	350	76
PE6040	350	81
PE6041	350	97
PE6043	350	5
PE6046	305	8
PE6057	305	2
PE6058	305	3
PE6059	305	13
PE6069	348	48
PE6070	347	11
PE6071	348	50
PE6072	348	49
PE6073	348	52
PE6075	349	92
PE6076	349	95
PE6077	348	52
PE6078	348	51
PE6079	348	55
PE6080	348	54
PE6081	349	1
PE6082	349	99
PE6083	349	7
PE6084	349	6
PE6085	347	4
PE6086	347	3
PE6087	347	6
PE6088	347	5
PE6089	349	14
PE6090	349	13
PE6091	349	18
PE6092	349	17
PE6095	349	26
PE6096	349	27
PE6097	349	24
PE6098	349	25
PE6099	349	28
PE6100	349	20
PE6101	349	33
PE6102	349	36
PE6103	349	38
PE6104	349	39
PE6105	349	30
PE6106	349	50

Model No.	Page	C/R
PE6107	349	45
PE6108	305	7
PE6109	305	9
PE6110	305	10
PE6111	305	11
PE6113	305	14
PE6114	305	15
PE6115	305	16
PE6116	306	20
PE6117	306	21
PE6118	306	22
PE6119	306	25
PE6120	306	26
PE6121	306	27
PE6122	306	29
PE6123	Web	
PE6124	306	31
PE6125	306	28
PE6126	306	30
PE6127	306	39
PE6128	306	41
PE6129	306	43
PE6130	306	45
PE6131	306	47
PE6132	306	49
PE6133	306	53
PE6134	306	52
PE6135	306	55
PE6136	306	54
PE6137	350	93
PE6138	349	29
PE6139	349	21
PE6140	349	40
PE6141	349	31
PE6143	Web	
PE6144	306	34
PE6146	347	7
PE6150	348	45
PE6151	Web	
PE6154	348	86
PE6156	348	84
PE6156A	348	85
PE6160	348	62
PE6161	348	60
PE6162	347	9
PE6163	347	8
PE6165	351	19
PE6168	350	99
PE6169	350	65
PE6172	349	11
PE6173	347	26
PE6174	347	24
PE6175	347	28
PE6176	348	72
PE6177	348	71
PE6178	347	21
PE6179	347	19
PE6180	348	70
PE6181	347	13
PE6182	347	22
PE6183	347	12
PE6184	347	1
PE6185	349	34
PE6186	349	23
PE6187	349	22
PE6188	350	69
PE6189	350	68
PE6190	348	79
PE6191	350	64
PE6193	306	38
PE6194	306	36
PE6195	306	37
PE6196	348	81
PE6197	350	91
PE6198	350	72
PE6199	348	41
PE6200	Web	
PE6201	Web	
PE6202-1001A	393	94
PE6202	351	18
PE6202-100PK	351	16
PE6202-25PK	351	17
PE6203	350	53
PE6204	350	54
PE6205	349	49
PE6206	350	51
PE6207	350	56
PE6208	350	57
PE6209	349	46
PE6210	349	47
PE6211	350	77
PE6212	350	80
PE6213	350	71
PE6214	350	75
PE6215	350	82
PE6216	350	83
PE6217	350	66
PE6218	350	67
PE6219	350	70
PE6220	350	7
PE6221	350	1
PE6222	350	3
PE6223	350	8
PE6224	351	9
PE6225	350	92
PE6226	350	96
PE6227	348	68
PE6228	349	48
PE6229	349	15
PE6230	351	11
PE6231	351	12
PE6232	350	78
PE6233	350	73
PE6234	350	74
PE6235	347	15
PE6236	347	14
PE6238	350	63
PE6239	350	95
PE6240	305	12
PE6241	348	46
PE6242	348	69
PE6243	348	67
PE6248	348	88
PE6249	348	89
PE6251	306	50
PE6800	393	73
PE6801	393	81
PE6802	393	86

Model No.	Page	C/R
PE6803	393	91
PE6804	393	96
PE6805	393	1
PE6806	393	6
PE6807	Web	
PE6808	Web	
PE6809	393	72
PE6810	393	80
PE6811	393	85
PE6812	393	93
PE6814	393	99
PE6815	393	5
PE6816	Web	
PE6818	393	75
PE6819	393	83
PE6820	393	89
PE6821	Web	
PE6823	393	3
PE6824	393	9
PE6826	Web	
PE6828	393	84
PE6829	Web	
PE6830	Web	
PE6831	Web	
PE6832	393	4
PE6833	393	10
PE6834	393	13
PE6835	393	16
PE6836	393	97
PE6TR000	351	23
PE6TR001	351	26
PE6TR002	348	57
PE6TR003	351	22
PE6TR004	351	20
PE6TR005	348	58
PE6TR006	Web	
PE6TR007	348	82
PE6TR008	348	83
PE6TR009	348	90
PE6TR010	348	87
PE6TR011	349	94
PE6TR012	348	91
PE6TR013	Web	
PE6TR014	349	10
PE6TR015	349	16
PE6TR016	349	12
PE6TR028	349	19
PE6TR029	350	70
PE6TR040	351	21
PE6TR041	349	9
PE6TR042	349	8
PE6T1000	350	58
PE6T1001	350	79
PE6T1002	350	6
PE6T1003	351	10
PE6T1004	351	13
PE6T1005	351	14
PE6T1006	351	15
PE6T1013	348	80
PE6T1014	348	47
PE6T1020	349	44
PE6T1021	349	43
PE6T1022	349	41
PE6T1023	349	42
PE6T1024	350	62
PE6T1025	350	61
PE6T1026	350	59
PE6T1027	350	60
PE6T1028	350	87
PE6T1029	350	86
PE6T1030	350	84
PE6T1031A	350	85
PE6T1032A	350	98
PE6T1032F	350	2
PE6T1033A	350	90
PE6T1033F	350	94
PE6T1035A	350	88
PE6T1035F	350	89
PE6T1036	349	98
PE6T1037	348	56
PE6T1038	348	44
PE6T1039	348	59
PE6T1040	348	61
PE6T1041	348	34
PE6T1042	348	35
PE6T1043	Web	
PE6T1044	348	36
PE6T1045	348	73
PE6T1046	348	74
PE6T1047	348	75
PE6T1048	348	76
PE6T1049	Web	
PE6T1050	348	42
PE6T1051	348	43
PE6T1052	349	97
PE6T1100	347	17
PE6T1101	347	16
PE6T1102	347	18
PE6T1103	347	22
PE6T1104	347	20
PE6T1105	347	23
PE6T1106	347	27
PE6T1107	347	25
PE6T1108	347	29
PE6T1109	348	30
PE6T1110	348	31
PE6T1111	348	32
PE6T1112	348	33
PE6T1113	348	63
PE6T1114	348	64
PE6T1115	348	65
PE6T1116	348	66
PE6T1117	348	37
PE6T1118	348	38
PE6T1119	348	39
PE6T1120	348	40
PE6T1121	348	77
PE6T1122	348	78
PE6T671	349	4
PE6T673	349	5
PE6T675	349	2
PE6T676	349	3
PE6T677	349	3
PE7000-1	75	12
PE7000-2	75	12
PE7000-3	75	12
PE7000-6	75	12
PE7000-10	75	12
PE7000-20	75	12

Model No.	Page	C/R
PE7000-30	75	12
PE7001-1	77	54
PE7001-2	77	54
PE7001-3	77	54
PE7001-4	77	54
PE7001-5	77	54
PE7001-6	77	54
PE7001-7	77	54
PE7001-8	77	54
PE7001-9	77	54
PE7001-10	77	54
PE7001-12	77	54
PE7001-15	77	54
PE7001-20	77	54
PE7001-30	77	54
PE7001-40	77	54
PE7002-1	75	13
PE7002-2	75	13
PE7002-3	75	13
PE7002-6	75	13
PE7002-10	75	13
PE7002-20	75	13
PE7002-30	75	13
PE7002-40	75	13
PE7003-1	75	16
PE7003-10	75	16
PE7003-20	75	16
PE7003-30	75	16
PE7003-40	75	16
PE7003-2	78	19
PE7003-3	78	19
PE7003-6	78	19
PE7004-1	76	26
PE7004-2	76	28
PE7004-3	76	30
PE7004-4	76	32
PE7004-5	76	34
PE7004-6	76	36
PE7004-7	76	38
PE7004-8	77	40
PE7004-9	77	42
PE7004-10	77	42
PE7004-12	77	44
PE7004-15	77	46
PE7004-20	77	48
PE7004-30	77	50
PE7004-40	77	52
PE7005-1	78	89
PE7005-2	78	91
PE7005-3	78	93
PE7005-4	78	95
PE7005-5	78	97
PE7005-6	78	99
PE7005-7	78	2
PE7005-8	78	4
PE7005-9	78	6
PE7005-10	78	6
PE7005-12	78	8
PE7005-15	78	10
PE7005-20	78	12
PE7005-30	78	14
PE7005-40	78	16
PE7006	352	27
PE7007	352	28
PE7008-3	88	55
PE7008-1	88	53
PE7008-2	88	55
PE7008-4	Web	
PE7008-5	88	55
PE7008-6	88	55
PE7009-1	87	46
PE7009-2	87	46
PE7009-3	87	46
PE7009-6	87	46
PE7009-10	87	46
PE7009-20	87	46
PE7009-30	87	46
PE7010-2	80	42
PE7010-3	80	42
PE7010-6	80	42
PE7010-10	80	42
PE7010-20	80	42
PE7010-30	80	42
PE7010-40	80	42
PE7013-1	79	27
PE7013-2	79	27
PE7013-3	79	27
PE7013-6	79	27
PE7013-10	79	27
PE7013-20	79	27
PE7013-30	79	27
PE7013-40	79	27
PE7014-1	79	25
PE7014-2	79	25
PE7014-3	79	25
PE7014-6	79	25
PE7014-10	79	25
PE7014-20	79	25
PE7014-30	79	25
PE7014-40	79	25
PE7015-1	80	45
PE7015-2	80	45
PE7015-3	80	45
PE7015-6	80	45
PE7015-10	80	45
PE7015-20	80	45
PE7015-30	80	45
PE7015-40	80	45
PE7016-1	80	47
PE7016-2	80	47
PE7016-3	80	47
PE7016-6	80	47
PE7016-10	80	47
PE7016-20	80	47
PE7016-30	80	47
PE7016-40	80	47
PE7017-1	81	62
PE7017-2	81	62
PE7017-3	81	62
PE7017-6	81	62
PE7017-10	81	62
PE7017-20	81	62
PE7017-30	82	62
PE7017-40	82	62
PE7018-1	82	67
PE7018-2	82	67
PE7018-3	82	67
PE7018-40	82	67
PE7019-6	83	4
PE7019-10	83	4
PE7019-20	83	4
PE7019-30	83	4
PE7019-40	83	4
PE7020-6	84	8
PE7020-10	84	8
PE7020-20	84	8
PE7020-30	84	8
PE7020-40	84	8
PE7021-6	85	23
PE7021-10	85	23
PE7021-20	85	23
PE7021-30	85	23
PE7021-40	85	23
PE7022-6	86	31
PE7022-10	86	31
PE7022-20	86	31
PE7022-30	86	31
PE7022-40	86	31
PE7024	Web	
PE7024-1	75	17
PE7024-2	75	17
PE7024-3	75	17
PE7024-6	75	17
PE7024-10	75	17
PE7024-20	75	17
PE7024-30	75	17
PE7024/SP-30	75	18
PE7025-2	80	41
PE7025-3	80	41
PE7025-6	80	41
PE7025-10	80	41
PE7025-20	80	41
PE7025-30	80	41
PE7025-40	80	41
PE7026-3	85	17
PE7026-6	85	17
PE7026-10	85	17
PE7026-20	85	17
PE7026-30	85	17
PE7026-40	85	17
PE7027	352	35
PE7028	352	40
PE7029-1	Web	
PE7029-3	87	47
PE7029-6	87	47
PE7029-10	87	47
PE7029-20	87	47
PE7029-30	87	47
PE7030-1	79	21
PE7030-2	79	21
PE7030-3	79	21
PE7030-6	79	21
PE7030-10	79	21
PE7030-20	79	21
PE7030-30	79	21
PE7031-2	Web	
PE7031-3	86	41
PE7031-6	Web	
PE7031-10	86	41
PE7031-20	Web	
PE7031-30	86	41
PE7032-6	87	42
PE7032-30	Web	
PE7034-1	89	58
PE7034-2	89	58
PE7034-6	89	58
PE7035-1	Web	
PE7035-2	89	63
PE7035-5	89	63
PE7039-1	Web	
PE7039-2	Web	
PE7039-3	79	22
PE7039-6	79	22
PE7039-10	79	22
PE7039-20	79	22
PE7039-30	79	22
PE7040-6	80	40
PE7040-10	80	40
PE7040-20	80	40
PE7040-30	Web	
PE7041-3	Web	
PE7041-6	Web	
PE7041-10	81	52
PE7041-20	Web	
PE7041-30	Web	
PE7042-10	83	78
PE7042-30	83	80
PE7042-20	Web	
PE7042-40	Web	
PE7043-10	Web	
PE7043-20	Web	
PE7043-30	Web	
PE7044-1	87	52
PE7044-2	88	52
PE7044-3	88	52
PE7044-6	88	52
PE7044-10	88	52
PE7044-20	88	52
PE7044-30	88	52
PE7045-1	77	87
PE7045-2	77	87
PE7045-3	77	87
PE7045-4	78	87
PE7045-5	78	87
PE7045-6	78	87
PE7045-7	78	87
PE7045-8	78	87
PE7045-9	78	87
PE7045-10	78	87
PE7045-12	78	87
PE7045-15	78	87
PE7045-20	78	87
PE7045-30	78	87
PE7045-40	78	87
PE7046-3	74	3
PE7046-6	74	5
PE7046-10	74	7
PE7046-20	74	7
PE7046-30	74	7
PE7047-1	Web	
PE7047-2	76	24
PE7047-3	76	24

Model No.	Page	C/R
PE7047-4	76	24
PE7047-5	76	24
PE7047-6	76	24
PE7047-7	76	24
PE7047-8	76	24
PE7047-9	76	24
PE7047-10	76	24
PE7047-12	76	24
PE7047-15	76	24
PE7047-20	76	24
PE7047-30	76	24
PE7047-40	76	24
PE7048-1	80	44
PE7048-2	80	44
PE7048-3	80	44
PE7048-6	80	44
PE7048-10	80	44
PE7048-20	80	44
PE7048-30	80	44
PE7048-40	80	44
PE7049-1	76	22
PE7049-2	76	22
PE7049-3	76	22
PE7049-6	76	22
PE7049-10	76	22
PE7049-20	76	22
PE7049-30	76	22
PE7050-1	Web	
PE7050-2	87	48
PE7050-3	87	48
PE7050-6	87	48
PE7050-10	87	48
PE7050-20	87	48
PE7050-30	87	48
PE7051-1	78	20
PE7051-2	78	20
PE7051-3	78	20
PE7051-6	78	20
PE7051-10	78	20
PE7051-20	78	20
PE7051-30	78	20
PE7051-40	78	20
PE7052-1	79	28
PE7052-2	79	28
PE7052-3	79	28
PE7052-6	79	28
PE7052-10	79	28
PE7052-20	79	28
PE7052-30	79	28
PE7053-1	Web	
PE7053-2	Web	
PE7053-3	Web	
PE7053-6	80	48
PE7053-10	80	48
PE7053-20	80	48
PE7053-30	Web	
PE7053-40	80	48
PE7054-1	Web	
PE7054-2	Web	
PE7054-3	Web	
PE7054-10	82	69
PE7054-20	82	69
PE7054-30	82	69
PE7054-40	Web	
PE7055-10	Web	
PE7055-20	Web	
PE7055-30	84	10
PE7055-40	84	10
PE7056-30	86	36
PE7056-40	Web	
PE7057-1	87	50
PE7057-2	87	50
PE7057-3	87	50
PE7057-6	87	50
PE7057-10	87	50
PE7061-6	89	65
PE7061-10	89	65
PE7061-20	89	65
PE7062-6	89	64
PE7062-10	89	64
PE7062-20	89	64
PE7063-6	89	66
PE7063-10	89	66
PE7063-20	89	66
PE7064-6	90	67
PE7064-10	90	67
PE7064-20	90	67
PE7066	352	30
PE7067	352	29
PE7068	352	31
PE7069	Web	
PE7070	352	36
PE7071	352	34
PE7072	352	32
PE7073	352	37
PE7074	352	39
PE7075	352	43
PE7076	352	45
PE7077	352	47
PE7078	352	49
PE7079	352	50
PE7081	352	51
PE7082	352	52
PE7083	352	41
PE7084-30	Web	
PE7085-2	87	43
PE7085-10	Web	
PE7085-20	87	43
PE7085-30	Web	
PE7087-0	78	18
PE7087-1	78	18
PE7087-2	78	18
PE7087-3	78	18
PE7087-4	78	18
PE7087-5	78	18
PE7087-6	78	18
PE7087-7	78	18
PE7087-8	78	18
PE7087-9	78	18
PE7087-10	78	18
PE7087-12	78	18
PE7087-15	78	18
PE7087-20	78	18
PE7087-30	78	18
PE7088-0	74	11
PE7088-1	74	11
PE7088-2	74	11
PE7088-3	74	11

Model No.	Page	C/R
PE7088-4	74	11
PE7088-5	74	11
PE7088-6	75	11
PE7088-7	75	11
PE7088-8	75	11
PE7088-9	75	11
PE7088-10	75	11
PE7088-12	75	11
PE7088-15	75	11
PE7088-20	75	11
PE7088-30	75	11
PE7089-0	74	10
PE7089-1	74	10
PE7089-2	74	10
PE7089-3	74	10
PE7089-4	74	10
PE7089-5	74	10
PE7089-6	74	10
PE7089-7	74	10
PE7089-8	74	10
PE7089-9	74	10
PE7089-10	74	10
PE7089-12	74	10
PE7089-15	74	10
PE7089-20	74	10
PE7089-30	74	10
PE7090-3

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE7202-40	85	19
PE7202-50	85	19
PE7202-60	85	19
PE7203-3	84	15
PE7203-6	84	15
PE7203-10	84	15
PE7203-20	84	15
PE7203-30	84	15
PE7203-40	84	15
PE7203-50	84	15
PE7203-60	84	15
PE7204-3	84	11
PE7204-6	84	11
PE7204-10	84	11
PE7204-20	84	11
PE7204-30	84	11
PE7204-40	84	11
PE7204-50	84	11
PE7204-60	84	11
PE7205-3	85	22
PE7205-6	85	22
PE7205-10	85	22
PE7205-20	85	22
PE7205-30	85	22
PE7205-40	85	22
PE7205-50	85	22
PE7205-60	85	22
PE7206-3	85	18
PE7206-6	85	18
PE7206-10	85	18
PE7206-20	85	18
PE7206-30	85	18
PE7206-40	85	18
PE7206-50	85	18
PE7206-60	85	18
PE7207-3	84	14
PE7207-6	84	14
PE7207-10	84	14
PE7207-20	84	14
PE7207-30	84	14
PE7207-40	84	14
PE7207-50	84	14
PE7207-60	84	14
PE7208-3	85	21
PE7208-6	85	21
PE7208-10	85	21
PE7208-20	85	21
PE7208-30	85	21
PE7208-40	85	21
PE7208-50	85	21
PE7208-60	85	21
PE7210-30	86	35
PE7211-3	84	16
PE7211-6	85	16
PE7211-10	85	16
PE7211-20	85	16
PE7211-30	85	16
PE7211-40	85	16
PE7211-50	85	16
PE7211-60	85	16
PE7212-3	84	13
PE7212-6	84	13
PE7212-10	84	13
PE7212-20	84	13
PE7212-30	84	13
PE7212-40	84	13
PE7212-50	84	13
PE7212-60	84	13
PE7213-3	86	26
PE7213-6	86	26
PE7213-10	86	26
PE7213-20	86	26
PE7213-30	86	26
PE7213-40	86	26
PE7213-50	86	26
PE7213-60	86	26
PE7214-3	85	20
PE7214-6	85	20
PE7214-10	85	20
PE7214-20	85	20
PE7214-30	85	20
PE7214-40	85	20
PE7214-50	85	20
PE7214-60	85	20
PE7216-50	Web	
PE7218-3	86	34
PE7221-3	86	30
PE7221-6	86	30
PE7221-10	86	30
PE7221-20	86	30
PE7221-40	86	30
PE7221-50	86	30
PE7221-60	86	30
PE7227-3	86	32
PE7227-6	86	32
PE7227-10	86	32
PE7227-20	86	32
PE7227-30	86	32
PE7227-40	86	32
PE7227-50	86	32
PE7227-60	86	32
PE7228-3	86	29
PE7228-20	86	29
PE7228-30	86	29
PE7228-50	Web	
PE7237-30	86	28
PE7301-1	327	80
PE7301-2	327	81
PE7301-200CART	328	23
PE7301-2000CART	328	24
PE7301-3	327	79
PE7301-4	327	77
PE7310-50	82	72
PE7310-3	82	72
PE7310-6	82	72
PE7310-10	82	72
PE7310-20	82	72
PE7310-30	82	72
PE7310-40	82	72
PE7311-50	83	83
PE7311-3	83	83
PE7311-6	83	83
PE7311-10	83	83
PE7311-20	83	83
PE7311-30	83	83
PE7311-40	83	83
PE7312-50	82	77
PE7312-3	82	77
PE7312-6	82	77
PE7312-10	83	79
PE7312-20	83	79
PE7312-30	83	81
PE7312-40	83	81
PE7313-50	82	71
PE7313-3	82	71
PE7313-6	82	71
PE7313-10	82	71
PE7313-20	82	71
PE7313-30	82	71
PE7313-40	82	71
PE7314-50	83	86
PE7314-3	83	86
PE7314-6	83	86
PE7314-10	83	86
PE7314-20	83	86
PE7314-30	83	86
PE7314-40	83	86
PE7315-50	83	82
PE7315-3	83	82
PE7315-6	83	82
PE7315-10	83	82
PE7315-20	83	82
PE7315-30	83	82
PE7315-40	83	82
PE7316-50	82	73
PE7316-3	82	75
PE7316-6	82	75
PE7316-10	82	75
PE7316-20	82	75
PE7316-30	82	75
PE7316-40	82	75
PE7317-50	83	85
PE7317-3	83	85
PE7317-6	83	85
PE7317-10	83	85
PE7317-20	83	85
PE7317-30	83	85
PE7317-40	83	85
PE7321-50	82	74
PE7321-3	82	76
PE7321-6	82	76
PE7321-10	82	76
PE7321-20	82	76
PE7321-30	82	76
PE7321-40	82	76
PE7322-50	83	3
PE7322-3	83	5
PE7322-6	83	5
PE7322-10	84	5
PE7322-20	84	5
PE7322-30	84	5
PE7322-40	84	5
PE7323-50	83	84
PE7323-3	83	84
PE7323-6	83	84
PE7323-10	83	84
PE7323-20	83	84
PE7323-30	83	84
PE7323-40	83	84
PE7337-50	84	6
PE7337-6	84	6
PE7337-10	84	6
PE7337-20	84	6
PE7337-30	84	6
PE7337-40	84	6
PE7337-50	84	6
PE7351-10	84	9
PE7351-20	84	9
PE7351-40	84	9
PE7351-50	84	9
PE7357-50	82	66
PE7357-3	82	68
PE7357-6	82	68
PE7357-10	82	68
PE7357-20	82	68
PE7357-30	82	68
PE7357-40	82	68
PE7363-6	82	64
PE7363-10	82	64
PE7363-20	82	64
PE7363-30	82	64
PE7363-40	82	64
PE7366-50	81	58
PE7366-3	81	58
PE7366-6	81	58
PE7366-10	81	58
PE7366-20	81	58
PE7366-30	81	58
PE7366-40	81	58
PE7367-50	82	60
PE7367-10	82	63
PE7367-3	82	63
PE7367-6	82	63
PE7367-20	82	63
PE7367-30	82	63
PE7367-40	82	63
PE7369-50	81	54
PE7369-6	81	54
PE7369-10	81	54
PE7369-20	81	54
PE7369-30	81	54
PE7369-40	81	54
PE7370-50	81	55
PE7370-3	81	55
PE7370-6	81	55
PE7370-10	81	55
PE7370-20	81	55
PE7370-30	81	55
PE7370-40	81	55
PE7371-50	81	56
PE7371-10	81	56
PE7371-3	81	56
PE7371-6	81	56
PE7371-20	81	56
PE7371-30	81	56
PE7371-40	81	56
PE7372-30	81	57
PE7375-20	82	70
PE7375-30	82	70
PE7375-40	82	70
PE7379-50	81	51
PE7379-3	81	51
PE7379-6	81	51
PE7379-10	81	53
PE7379-20	81	53
PE7379-30	81	53
PE7379-40	81	53
PE7380-50	81	50
PE7380-3	81	50
PE7380-6	81	50
PE7380-10	81	50
PE7380-20	81	50
PE7380-30	81	50
PE7380-40	81	50
PE7385-3	85	24
PE7385-6	85	24
PE7385-10	85	24
PE7385-20	85	24
PE7385-30	85	24
PE7385-40	85	24
PE7386-3	80	43
PE7386-6	80	43
PE7386-10	80	43
PE7386-15	80	43
PE7386-20	80	43
PE7386-30	80	43
PE7386-40	80	43
PE7387-10	86	38
PE7387-20	86	38
PE7387-30	86	38
PE7387-40	86	38
PE7388-3	83	87
PE7388-6	83	89
PE7388-10	83	91
PE7388-15	83	93
PE7388-20	83	95
PE7388-30	83	97
PE7388-40	83	99
PE7389-3	83	88
PE7389-6	83	90
PE7389-10	83	92
PE7389-15	83	94
PE7389-20	83	96
PE7389-30	83	98
PE7389-40	83	1
PE7390-1	79	23
PE7390-2	79	23
PE7390-3	79	23
PE7390-6	79	23
PE7390-10	79	23
PE7390-15	79	23
PE7390-20	79	23
PE7390-30	79	23
PE7391-6	79	26
PE7391-10	79	26
PE7391-20	79	26
PE7391-30	79	26
PE7391-1	79	26
PE7391-2	79	26
PE7391-3	79	26
PE7391-15	79	26
PE7392-1	81	59
PE7392-2	81	59
PE7392-3	81	59
PE7392-6	81	59
PE7392-10	81	59
PE7392-20	81	59
PE7392-30	81	59
PE7392-40	81	59
PE7393-3	82	65
PE7393-10	82	65
PE7393-20	82	65
PE7393-30	82	65
PE7393-40	82	65
PE7394-2	83	2
PE7394-3	83	2
PE7394-6	83	2
PE7394-10	83	2
PE7394-30	83	2
PE7394-40	83	2
PE7395-0	76	21
PE7395-1	76	21
PE7395-2	76	21
PE7395-3	76	21
PE7395-4	76	21
PE7395-5	76	21
PE7395-6	76	21
PE7395-7	76	21
PE7395-8	76	21
PE7395-9	76	21
PE7395-10	76	21
PE7395-12	76	21
PE7395-15	76	21
PE7395-20	76	21
PE7396-1	87	51
PE7396-2	87	51
PE7396-3	87	51
PE7396-4	87	51
PE7396-5	87	51
PE7396-6	87	51
PE7396-7	87	51
PE7396-8	87	51
PE7396-9	87	51
PE7396-10	87	51
PE7396-16	87	51
PE7396-20	87	51
PE7403-1	74	9
PE7403-2	74	9
PE7403-3	74	9
PE7403-4	74	9
PE7403-5	74	9
PE7403-6	74	9
PE7403-7	74	9
PE7403-8	74	9
PE7403-9	74	9
PE7403-10	74	9
PE7403-20	74	9
PE7403-30	74	9
PE7411-3	Web	
PE7421-3	85	25
PE7421-6	85	25
PE7421-10	85	25
PE7421-20	85	25
PE7421-30	85	25
PE7421-40	85	25
PE7422	90	68
PE7423-30	87	45
PE7423-40	87	45
PE7424-10	86	27
PE7424-20	86	27
PE7424-30	86	27
PE7424-40	86	27
PE7424-03	86	27
PE7424-06	86	27
PE7425-10	86	33
PE7425-20	86	33
PE7425-30	86	33
PE7425-40	86	33
PE7426-03	81	61
PE7426-06	81	61
PE7426-10	81	61
PE7426-20	81	61
PE7426-30	81	61
PE7426-40	81	61
PE7427-03	84	7
PE7427-10	84	7
PE7427-15	84	7
PE7427-20	84	7
PE7427-30	84	7
PE7427-40	84	7
PE7427-06	84	7
PE7428-01	80	46
PE7428-02	80	46
PE7428-03	80	46
PE7428-06	80	46
PE7428-10	80	46
PE7428-15	80	46
PE7428-20	80	46
PE7428-30	80	46
PE7429-0	74	1
PE7429-1	74	1
PE7429-2	74	1
PE7429-3	74	1
PE7429-4	74	1
PE7429-5	74	1
PE7429-6	74	1
PE7429-7	74	1
PE7429-8	74	1
PE7429-9	74	1
PE7429-10	74	1
PE7429-12	74	1
PE7429-15	74	1
PE7429-20	74	1
PE7429-30	74	1
PE7430-0	75	19
PE7430-1	75	19
PE7430-2	75	19
PE7430-3	75	19
PE7430-4	75	19
PE7430-5	75	19
PE7430-6	75	19
PE7430-7	75	19
PE7430-8	75	19
PE7430-9	75	19
PE7430-10	75	19
PE7430-12	75	19
PE7430-15	75	19
PE7430-20	76	19
PE7430-30	76	19
PE7437-1	76	23
PE7437-2	76	23
PE7437-3	76	23
PE7437-4	76	23
PE7437-5	76	23
PE7437-6	76	23
PE7437-7	76	23
PE7437-8	76	23
PE7437-9	76	23
PE7437-10	76	23
PE7437-15	76	23
PE7437-20	76	23
PE7437-30	76	23
PE7438-1	87	49
PE7438-2	87	49
PE7438-3	87	49
PE7438-4	87	49
PE7438-5	87	49
PE7438-6	87	49
PE7438-7	87	49
PE7438-8	87	49
PE7438-9	87	49
PE7438-10	87	49
PE7438-20	87	49
PE70A1000	91	7
PE70A1001	88	56
PE70A1008	88	57
PE70A1009	77	57
PE70A1010	77	59
PE70A1011	77	58
PE70A1012	77	60
PE70A1013	Web	
PE70A1014	77	55
PE70A1015	77	56
PE70A1016	Web	
PE70A1017	91	5
PE70A1021	88	54
PE70A1022	89	60
PE70A1023	89	62
PE70A1024	89	59
PE70A1025	89	61
PE70A1031	91	6
PE70A2000	91	9
PE70A2001	91	10
PE70A2002	91	11
PE70A2003	91	12
PE70A2900	91	8
PE70A3900	91	2
PE70A3901	91	3
PE70A3902	91	4
PE70A4000	91	85
PE70A5000	91	91
PE70A5001	91	92
PE70A5002	91	93
PE70A5003	90	69
PE70A5004	91	87
PE70A5005	91	89
PE70A5006	91	88
PE70A5007	91	90
PE70A5008	91	98
PE70A5009	91	94
PE70A5010	91	95
PE70A5011	91	96
PE70A5012	91	86
PE70A5013	91	1
PE70A6000	91	97
PE70A6001	91	99
PE70A8000	90	71
PE70A8001	90	70
PE70A8002	90	75
PE70A8003	90	72
PE70A8004	90	73
PE70A8005	90	74
PE70A8006	91	83
PE70A8007	90	78
PE70A8008	91	80
PE70A8009	91	81
PE70A8010	91	82
PE70A8011	91	84
PE70A8012	90	79
PE70A8013	90	76
PE70A8014	90	77
PE70A9000	91	13
PE70A9001	91	14
PE70A9002	91	15
PE70A9003	91	16
PE70A9004	92	17
PE70A9005	92	18
PE70A9006	92	19
PE70A9007	92	20
PE70A9008	92	21
PE70A9009	92	22
PE70A9010	92	23
PE70A9011	92	24
PE70A9012	92	25
PE70A9013	92	26
PE70A9014	92	27
PE70A9015	92	28
PE70A9016	92	29
PE70A9017	92	30
PE70A9018	92	31
PE70MP1001	352	38
PE70MP1002	352	33
PE70MP1004	352	48
PE70MP1005	352	46
PE70MP1006	352	44
PE70MP1007	352	42
PE70MP5000	353	18
PE71S1100	340	1
PE71S1101	340	3
PE71S1102	340	5
PE71S1103	340	7
PE71S1104	340	9
PE71S1105	340	2
PE71S1106	340	4
PE71S1107	340	6
PE71S1108	340	8
PE71S1109	340	10
PE71S2007	335	79
PE71S2008	335	65
PE71S2009	336	18
PE71S2010	336	97
PE71S2011	335	80
PE71S2012	335	66
PE71S2013	336	19
PE71S2014	336	98
PE71S2015	336	87
PE71S2016	335	73
PE71S2017	337	29
PE71S2018	336	6
PE71S2019	336	88
PE71S2020	335	74
PE71S2021	337	30
PE71S2022	336	7
PE71S2023	335	81
PE71S2024	335	67
PE71S2032	338	76
PE71S2033	338	78
PE71S2034	339	83
PE71S2035	336	95
PE71S2036	336	93
PE71S2037	337	53
PE71S2038	336	20
PE71S2039	336	13
PE71S2040	336	14
PE71S2041	336	3
PE71S2042	336	15
PE71S2043	336	92
PE71S2044	337	52
PE71S2045	338	75
PE71S2046	338	77
PE71S2047	336	16
PE71S2048	336	17
PE71S2050	336	99
PE71S3900	339	98
PE71S3901	340	99
PE71S5000	339	93
PE71S5001	339	91
PE71S5002	339	94
PE71S5003	339	96
PE71S5004	339	97
PE71S5005	339	92
PE71S5006	339	95
PE71S6052	334	34
PE71S6053	334	35
PE71S6054	334	36
PE71S6055	334	37
PE71S6056	334	48
PE71S6057	334	49
PE71S6058	329	18
PE71S6059	329	19
PE71S6060	331	7
PE71S6061	Web	
PE71S6062	Web	
PE71S6063	331	12
PE71S6064	332	61
PE71S6065	332	76
PE71S6066	332	77
PE71S6067	332	79
PE71S6068	332	80
PE71S6069	332	78
PE71S6070	332	75
PE71S6071	332	81
PE71S6072	331	97
PE71S6073	331	98
PE71S6074	333	2
PE71S6075	333	7
PE71S6076	331	25
PE71S6077	333	3
PE71S6078	332	66
PE71S6079	332	52
PE71S6080	331	23
PE71S6081	Web	
PE71S6082	331	99
PE71S6083	331	26
PE71S6084	332	65
PE71S6085	334	33
PE71S6086	Web	
PE71S6087	334	46
PE71S6088	334	47
PE71S6089	Web	
PE71S6091	Web	
PE71S6092	334	54
PE71S6093	Web	
PE71S6094	Web	
PE71S6095	Web	
PE71S6096	Web	
PE71S6097	Web	
PE71S6098	330	61
PE71S6099	Web	
PE71S6100	Web	
PE71S6101	Web	
PE71S6102	Web	
PE71S6103	330	63
PE71S6104	Web	
PE71S6105	Web	
PE71S6106	330	65
PE71S6107	Web	
PE71S6108	Web	
PE71S6109	330	64
PE71S6110	330	62
PE71S6111	Web	
PE71S6112	Web	
PE71S6113	Web	
PE71S6114	Web	
PE71S6115	Web	
PE71S6116	Web	
PE71S6117	Web	
PE71S6118	Web	
PE71S6119	Web	
PE71S6120	Web	
PE71S6121	Web	
PE71S6122	330	77
PE71S6123	330	78
PE71S6124	Web	
PE71S6125	Web	
PE71S6126	Web	
PE71S6127	Web	
PE71S6128	Web	
PE71S6129	Web	
PE71S6130	330	57
PE71S6131	330	58
PE71S6132	Web	
PE71S6133	Web	
PE71S6134	Web	
PE71S6135	Web	
PE71S6136	Web	
PE71S6137	330	71
PE71S6138	Web	
PE71S6139	Web	
PE71S6140	330	66
PE71S6141	Web	
PE71S6142	Web	
PE71S6143	330	76
PE71S6144	Web	
PE71S6145	Web	
PE71S6146	Web	
PE71S6147	Web	
PE71S6148	Web	
PE71S6149	Web	
PE71S6150	329	20
PE71S6151	Web	
PE71S6152	Web	
PE71S6153	Web	
PE71S6154	Web	
PE71S6155	329	26
PE71S6156	329	23
PE71S6157	329	24
PE71S6158	329	21
PE71S6159	329	22
PE71S6160	329	16
PE71S6161	329	17
PE71S6162	329	27
PE71S6163	329	28
PE71S6164	329	25
PE71S6165	Web	
PE71S6166	329	34
PE71S6167	329	35
PE71S6168	329	29
PE71S6169	329	30
PE71S6170	329	42
PE71S6171	329	43
PE71S6172	329	39
PE71S6173	Web	
PE71S6174	Web	
PE71S6175	329	36
PE71S6176	Web	
PE71S6177	329	31
PE71S6178	329	44
PE71S6179	329	45
PE71S6180	329	40
PE71S6181	329	41
PE71S6182	Web	
PE71S6183	329	7
PE71S6184	328	4
PE71S6185	329	5
PE71S6186	329	12
PE71S6187	329	13
PE71S6188	Web	
PE71S6189	329	9
PE71S6190	Web	
PE71S6191	329	8
PE71S6192	329	6
PE71S6193	Web	
PE71S6194	329	14
PE71S6195	329	15
PE71S6196	329	10
PE71S6197	329	11
PE71S6198	Web	
PE71S6199	328	3
PE71S6200	328	2
PE71S6201	Web	
PE71S6202	329	37
PE71S6203	329	38
PE71S6204	329	32
PE71S6205	329	33
PE71S6206	Web	
PE71S6207	328	1
PE71S6208	336	5
PE71S6209	335	68
PE71S6210	336	1
PE71S6211	337	35
PE71S6212	338	55
PE71S6213	338	79
PE71S6214	335	69
PE71S6215	336	2
PE71S6216	337	36
PE71S6217	338	56
PE71S6218	339	80
PE71S6219	337	28
PE71S6220	336	82
PE71S6221	337	23
PE71S6222	337	44
PE71S6223	338	65
PE71S6224	339	81
PE71S6225	336	83
PE71S6226	337	24
PE71S6227	337	45
PE71S6228	338	66
PE71S6229	339	82
PE71S6230	335	64
PE71S6231	335	70
PE71S6232	335	72
PE71S6233	335	75
PE71S6234	335	76
PE71S6235	335	77
PE71S6236	335	71
PE71S6237	336	94
PE71S6238	336	8
PE71S6239	336	9
PE71S6240	336	10
PE71S6241	336	4
PE71S6242	337	34
PE71S6243	337	37
PE71S6244	337	39
PE71S6245	337	40
PE71S6246	337	41
PE71S6247	337	42
PE71S6248	337	38
PE71S6249	337	54
PE71S6250	338	57
PE71S6251	338	59
PE71S6252	338	60
PE71S6253	338	61
PE71S6254	338	62
PE71S6255	338	58
PE71S6258	335	78
PE71S6259	336	84
PE71S6260	336	86
PE71S6261	336	89
PE71S6262	336	90
PE71S6263	336	91
PE71S6264	336	85
PE71S6265	336	12
PE71S6266	337	31
PE71S6267	337	32
PE71S6268	337	33
PE71S6269	337	27
PE71S6270	337	43
PE71S6271	337	46
PE71S6272	337	48
PE71S6273	337	49
PE71S6274	337	50
PE71S6275	337	51
PE71S6276	337	47
PE71S6277	338	63
PE71S6278	338	67
PE71S6279	338	69
PE71S6280	338	71
PE71S6281	338	73
PE71S6282	338	74
PE71S6283	338	68
PE71S6284	338	70
PE71S6285	338	72
PE71S6286	339	84
PE71S6287	339	85
PE71S6288	339	87
PE71S6289	339	88
PE71S6290	339	89
PE71S6291	339	90
PE71S6292	339	86
PE71S6293	329	46
PE71S6294	Web	
PE71S6295	Web	
PE71S6296	Web	
PE71S6297	Web	
PE71S6298	329	48
PE71S6299	Web	
PE71S6300	329	47
PE71S6301	329	52
PE71S6302	329	50
PE71S6303	Web	
PE71S6304	329	51
PE71S6305	Web	
PE71S6306	329	49
PE71S6307	Web	
PE71S6308	Web	
PE71S6309	330	59
PE71S6310	330	60
PE71S6311	Web	
PE71S6312	Web	
PE71S6313	329	55
PE71S6314	329	56
PE71S6315	329	53
PE71S6316	329	54
PE71S6317	330	70
PE71S6318	330	69
PE71S6319	330	67
PE71S6320	330	68
PE71S6321	330	72
PE71S6322	330	73
PE71S6323	330	74
PE71S6324	330	75
PE71S6326	Web	
PE71S6327	Web	
PE71S6328	Web	
PE71S6329	332	73
PE71S6330	332	74
PE71S6331	334	44
PE71S6332	334	31
PE71S6333	334	42
PE71S6334	333	29
PE71S6335	334	38
PE71S6336	334	40
PE71S6337	334	39
PE71S6338	334	41
PE71S6339	334	45
PE71S6340	334	32
PE71S6341	334	43
PE71S6342	333	30
PE71S6344	Web	
PE71S6345	Web	
PE71S6346	Web	
PE71S6347	331	4
PE71S6348	330	85
PE71S6349	333	83
PE71S6350	331	11
PE71S6351	331	3
PE71S6352	333	94
PE71S6353	333	89
PE71S6354	331	8
PE71S6355	331	9
PE71S6356	331	38
PE71S6357	331	39

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE71S8005	337	26
PE71S8006	337	25
PE71S8007	336	11
PE71S8008	337	22
PE71S8009	336	96
PE71S9001	390	46
PE71S9002	390	47
PE71S9003	390	44
PE71S9004	390	45
PE73SP1000	327	95
PE73SP1001	327	5
PE73SP1002	327	6
PE73SP1003	327	7
PE73SP1004	327	66
PE73SP1005	327	71
PE73SP1006	327	69
PE73SP1007	327	70
PE73SP1008	327	68
PE73SP1010	327	97
PE73SP1011	327	14
PE73SP1013	327	98
PE73SP1014	327	99
PE73SP1015	327	87
PE73SP1016	327	19
PE73SP1017	327	75
PE73SP1018	327	88
PE73SP1019	327	94
PE73SP1021	327	93
PE73SP1022	327	92
PE73SP1023	327	12
PE73SP1024	327	86
PE73SP1025	327	85
PE73SP1026	327	22
PE73SP1027	327	83
PE73SP1028	327	9
PE73SP1029	327	91
PE73SP1030	327	84
PE73SP1031	327	11
PE73SP1032	327	21
PE73SP1033	327	20
PE73SP1034	327	72
PE73SP1035	327	90
PE73SP1036	327	10
PE73SP1037	327	65
PE73SP1038	327	82
PE73SP1039	327	78
PE73SP1040	327	76
PE73SP1041	327	4
PE73SP1042	327	3
PE73SP1043	313	7
PE73SP1044	313	8
PE73SP1045	313	5
PE73SP1046	313	6
PE73SP1047	313	9
PE73SP1048	327	2
PE73SP1049	327	8
PE73SP1050	327	1
PE73SP1051	326	60
PE73SP1060	327	64
PE73SP1061	327	61
PE73SP1062	327	62
PE73SP1063	327	67
PE73SP1064	327	74
PE73SP1065	327	96
PE73SP1066	327	13
PE73SP1067	327	16
PE73SP1068	327	15
PE73SP1069	327	17
PE73SP1070	327	63
PE73SP1071	327	73
PE73SP1072	327	20
PE73SP1073	327	18
PE7AP006-01	79	24
PE7AP006-02	79	24
PE7AP006-03	79	24
PE7AP006-04	79	24
PE7AP006-05	79	24
PE7AP006-06	79	24
PE7AP006-09	79	24
PE7AP006-10	79	24
PE7AP006-12	79	24
PE7AP006-15	79	24
PE7AP006-20	79	24
PE7AP006-30	79	24
PE7AP006-40	79	24
PE7AP1000-0	75	15
PE7AP1000-1	75	15
PE7AP1000-2	75	15
PE7AP1000-3	75	15
PE7AP1000-6	75	15
PE7AP1000-9	75	15
PE7AP1000-12	75	15
PE7AP1000-15	75	15
PE7AP1000-18	75	15
PE7AP1000-20	75	15
PE7AP1001-3	80	49
PE7AP1001-6	80	49
PE7AP1001-10	81	49
PE7AP1001-20	81	49
PE7AP1002-0	75	14
PE7AP1002-1	75	14
PE7AP1002-2	75	14
PE7AP1002-3	75	14
PE7AP1002-6	75	14
PE7AP1002-9	75	14
PE7AP1002-12	75	14
PE7AP1002-15	75	14
PE7AP1002-20	75	14
PE7AP150-03	86	37
PE7AP150-06	86	37
PE7AP150-10	86	37
PE7AP150-20	86	37
PE7AP150-30	86	37
PE7AP150-40	86	37
PE7AP200-20	86	39
PE7AP250-10	86	40
PE7AP250-20	86	40
PE7AP250-30	86	40
PE7AP250-40	86	40
PE7AP4009-03	79	29
PE7AP4009-06	79	31
PE7AP4009-10	80	33
PE7AP4009-20	80	35
PE7AP4009-30	80	37
PE7AP4009-40	80	39
PE7AP402-3	79	30
PE7AP402-6	79	32
PE7AP402-10	80	34
PE7AP402-20	80	36
PE7AP402-30	80	38
PE7AP412-00	74	2
PE7AP412-01	74	2
PE7AP412-02	74	2
PE7AP412-03	74	2
PE7AP412-04	74	4
PE7AP412-05	74	4
PE7AP412-06	74	4
PE7AP412-08	74	6
PE7AP412-09	74	6
PE7AP412-10	74	8
PE7AP412-12	74	8
PE7AP412-15	74	8
PE7AP412-20	74	8
PE7AP412-30	74	8
PE7AP418-10	87	44
PE7AP418-20	87	44
PE7AP418-30	87	44
PE7AP418-40	87	44
PE7AP418-03	87	44
PE7SM1000A	335	63
PE8001	319	94
PE8001-P	319	95
PE8002	319	96
PE8002-P	319	97
PE8003	319	98
PE8003-P	319	99
PE8004-P	319	2
PE8005	319	3
PE8005-P	319	4
PE8006	319	5
PE8006-P	319	6
PE8007	319	7
PE8007-P	319	8
PE8008	319	9
PE8008-P	319	10
PE8009	319	11
PE8009-P	319	12
PE8010	320	22
PE8011	Web	
PE8238	Web	
PE8241	Web	
PE8243	Web	
PE8012	320	23
PE8012-P	320	25
PE8012P	320	24
PE8013	320	27
PE8014	320	28
PE8015	320	29
PE8016	320	30
PE8017	318	73
PE8018	318	74
PE8019	318	75
PE8020	318	76
PE8021	318	77
PE8022	318	78
PE8023	318	79
PE8024	318	80
PE8025	318	81
PE8026	318	82
PE8027	318	83
PE8028	319	84
PE8029	319	85
PE8030	319	86
PE8031	319	87
PE8032	319	88
PE8033	319	89
PE8034	319	90
PE8035	319	91
PE8036	319	92
PE8037	319	93
PE8040	319	15
PE8044	319	1
PE8203	322	5
PE8210	93	88
PE8211	93	89
PE8212	93	90
PE8213	93	79
PE8214	93	80
PE8215	93	81
PE8216	93	70
PE8217	93	71
PE8218	93	72
PE8219	93	97
PE8220	93	98
PE8221	93	99
PE8222	93	63
PE8223	93	64
PE8224	93	65
PE8225	93	66
PE8226	93	67
PE8227	93	68
PE8231	93	4
PE8232	93	5
PE8233	93	6
PE8234	93	11
PE8236	93	10
PE8237	93	60
PE8239	93	61
PE8240	93	8
PE8242	93	9
PE8244	323	10
PE8245	323	11
PE8246	323	12
PE8247	323	13
PE8250	93	91
PE8251	93	82
PE8252	93	1
PE8253	323	15
PE8255	323	14
PE8258	93	59
PE8260	93	10
PE8261	93	7
PE8262	93	13
PE8263	93	73
PE8264	93	2
PE8265	93	83
PE8266	93	92
PE8267	93	69
PE8268	93	62
PE8269	93	78
PE8270	93	74
PE8271	93	84
PE8272	93	3
PE8273	93	93
PE8274	93	75
PE8275	93	76
PE8276	93	85
PE8277	93	94
PE8278	93	95
PE8279	93	96
PE8280	93	86
PE8281	93	87
PE8282	93	77
PE8300	226	14
PE8301	226	19
PE8302	226	27
PE8303	226	36
PE8304	226	38
PE8305	226	43
PE8306	226	47
PE8310	226	95
PE8311	226	1
PE8312	226	3
PE8313	226	5
PE8314	226	26
PE8315	226	35
PE8316	226	24
PE8317	226	25
PE8318	226	46
PE8319	226	89
PE8320	225	86
PE8321	226	6
PE8322	226	90
PE8323	226	7
PE8324	226	91
PE8325	226	9
PE8326	226	93
PE8327	226	23
PE8328	226	34
PE8400	224	42
PE8401	225	49
PE8402	225	55
PE8403	225	60
PE8404	225	66
PE8405	225	68
PE8406	224	24
PE8410	224	29
PE8411	224	29
PE8412	224	31
PE8413	224	33
PE8414	224	46
PE8415	224	26
PE8416	226	16
PE8417	226	99
PE8418	224	38
PE8419	224	22
PE8420	226	10
PE8421	226	94
PE8422	224	36
PE8423	224	20
PE8424	226	8
PE8425	226	92
PE8426	224	34
PE8427	224	18
PE8428	224	37
PE8431	224	21
PE8432	225	51
PE8433	225	57
PE8501	322	90
PE8503	322	95
PE8504	322	98
PE8505	322	86
PE8506	322	91
PE8507	322	93
PE8508	322	96
PE8509	322	99
PE8600	318	53
PE8601	318	54
PE8602	318	57
PE8603	318	58
PE8650	316	4
PE8652	316	5
PE8653	316	6
PE8654	316	30
PE8700	314	12
PE8701	314	22
PE8702	314	28
PE8703	314	15
PE8704	314	14
PE8705	314	10
PE8706	314	11
PE8707	314	17
PE8708	314	19
PE8709	314	18
PE8710	314	16
PE8711	314	21
PE8712	314	23
PE8713	314	24
PE8714	314	26
PE8715	315	47
PE8716	315	46
PE8717	315	45
PE8718	315	48
PE8719	315	52
PE8720	315	57
PE8721	315	58
PE8722	315	53
PE8723	315	51
PE8724	315	54
PE8725	315	59
PE8726	315	55
PE8727	315	56
PE8728	313	94
PE8729	313	95
PE8730	313	96
PE8731	313	97
PE8732	313	98
PE8733	313	99
PE8734	313	1
PE8735	313	2
PE8736	313	3
PE8738	313	4
PE8739	314	25
PE8740	314	27
PE8741	314	29
PE8742	314	30
PE8743	314	40
PE8747	314	44
PE80L1000	318	60
PE80L1001	318	63
PE80L2000	318	67
PE80L2001	318	64
PE80L2002	318	70
PE80L2003	318	59
PE80L2004	318	68
PE80L2005	318	62
PE80L2006	318	66
PE80L2007	318	71
PE80L2008	318	72
PE80L2009	318	61
PE80L3000	318	65
PE80L4000	318	69
PE80P1000	320	21
PE80P1001	320	19
PE80P1002	320	20
PE80T1000	320	31
PE80T1001	320	32
PE80T1002	320	33
PE80T1003	320	26
PE80T1004	319	13
PE80T1005	319	14
PE80T3000	384	6
PE80T3001	384	5
PE80T3002	384	4
PE80T3003	384	3
PE80T3004	384	2
PE80T3005	384	1
PE80T4000	320	16
PE80T4001	320	18
PE80T4002	320	17
PE80T6000	320	34
PE80T6001	320	35
PE80T6002	321	36
PE80T6003	321	37
PE80T6004	321	40
PE80T6005	321	41
PE80T6006	321	48
PE80T6007	321	49
PE80T6008	321	54
PE80T6009	321	55
PE80T6010	321	38
PE80T6011	321	39
PE80T6012	321	42
PE80T6013	321	43
PE80T6014	321	44
PE80T6015	321	45
PE80T6016	321	46
PE80T6017	321	47
PE80T6018	321	50
PE80T6019	321	51
PE80T6020	321	52
PE80T6021	321	53
PE80T6022	321	56
PE80T6023	321	57
PE80T6024	321	58
PE80T6025	321	59
PE82P1000	322	9
PE82P2000	323	16
PE82P2001	323	17
PE82P5000	322	7
PE82P5001	Web	
PE82P5003	322	6
PE83CR000	225	59
PE83CR001	224	39
PE83CR002	225	64
PE83CR003	224	43
PE83CR004	224	44
PE83CR005	225	50
PE83CR006	225	56
PE83CR007	224	40
PE83CR1000	224	41
PE83CR1001	224	23
PE83CR1002	224	45
PE83CR1003	224	25
PE83CR1004	224	47
PE83CR1005	224	27
PE83CR1006	225	54
PE83CR1007	224	30
PE83CR1008	225	58
PE83CR1009	224	32
PE83CR1010	225	62
PE83CR1011	225	65
PE83CR1012	225	67
PE83CR1013	224	6
PE83CR1014	224	1
PE83CR1015	224	7
PE83CR1016	224	2
PE83CR1017	224	8
PE83CR1018	224	3
PE83CR1019	224	9
PE83CR1020	224	4
PE83CR1021	224	10
PE83CR1022	224	5
PE83CR1023	224	11
PE83CR1024	224	12
PE83CR1025	224	13
PE83CR1026	225	61
PE83CR1027	224	14
PE83CR1028	224	15
PE83CR1029	224	17
PE83CR1030	224	48
PE83CR1031	224	28
PE83CR1032	224	16
PE83CR1033	225	52
PE83CR1034	225	53
PE83IR000	226	37
PE83IR001	226	39
PE83IR002	226	13
PE83IR003	226	96
PE83IR004	226	18
PE83IR005	226	20
PE83IR006	226	28
PE83IR007	226	11
PE83IR1000	226	15
PE83IR1001	226	97
PE83IR1002	226	17
PE83IR1003	226	98
PE83IR1004	226	21
PE83IR1005	226	2
PE83IR1006	226	30
PE83IR1007	226	4
PE83IR1010A	226	40
PE83IR1011	226	44
PE83IR1012	226	49
PE83IR1013	225	74
PE83IR1014	225	69
PE83IR1015	225	75
PE83IR1016	225	70
PE83IR1017	225	76
PE83IR1018	225	71
PE83IR1019	225	77
PE83IR1020	225	72
PE83IR1021	225	78
PE83IR1022	225	73
PE83IR1023	225	79
PE83IR1024	225	80
PE83IR1025	225	81
PE83IR1026	226	41
PE83IR1027	226	42
PE83IR1028	226	45
PE83IR1029	226	31
PE83IR1030	226	32
PE83IR1031	226	33
PE83IR1032	226	12
PE83IR1033	225	83
PE83IR1034	226	48
PE83IR1035	225	85
PE83IR1036	226	87
PE83IR1037	226	88
PE83IR1038	225	82
PE83IR1039	226	22
PE83IR1040	226	29
PE83IR1041	225	84
PE85N1000	321	63
PE85N1001	321	60
PE85N1002	321	78
PE85N1003	321	79
PE85N1004	322	88
PE85N1005	322	89
PE85N1006	321	82
PE85N1007	321	83
PE85N1008	321	84
PE85N1009	321	85
PE85N1010	321	64
PE85N1011	321	71
PE85N1012	321	74
PE85N1013	321	81
PE85N1014	322	92
PE85N1015	322	94
PE85N1016	322	97
PE85N1017	321	70
PE85N1018	321	75
PE85N1019	321	61
PE85N1020	321	62
PE85N1021	321	80
PE85N1022	322	87
PE85NS4000	321	65
PE85NS4001	321	66
PE85NS4002	321	68
PE85NS4003	321	67
PE85NS4004	321	69
PE85NS5000	321	72
PE85NS5001	321	76
PE85NS5002	321	73
PE85NS5003	321	77
PE86GM2000	317	31
PE86GM2001	317	32
PE86GM2003	317	33
PE86GM2004	317	35
PE86GM2005	317	36
PE86GM2006	317	37
PE86GM2007	317	38
PE86GM2008	317	39
PE86X1000	316	19
PE86X1001	316	21
PE86X1002	Web	
PE86X1003	316	14
PE86X1004	316	17
PE86X1005	Web	
PE86X1006	316	10
PE86X1007	316	12
PE86X1008	316	11
PE86X1009	316	16
PE86X1010	316	22
PE86X1013	316	91
PE86X1014	316	94
PE86X1015	316	95
PE86X1016	316	96
PE86X1017	316	1
PE86X1018	316	2
PE86X1019	316	92
PE86X1020	316	93
PE86X1021	316	97
PE86X1022	316	98
PE86X1023	316	3
PE86X1024	316	6
PE86X1025	316	7
PE86X1026	316	8
PE86X1027	316	9
PE86X1028	316	13
PE86X1029	316	15
PE86X1030	316	18
PE86X1031	316	20
PE86X1032	316	29
PE86X9000	316	23
PE86X9001	316	24
PE86X9002	316	25
PE86X9003	316	26
PE86X9004	316	27
PE86X9005	316	28
PE86X9006	316	28
PE87FL1000	314	31
PE87FL1001	314	32
PE87FL1002	314	34
PE87FL1003	314	33
PE87FL1004	314	35
PE87FL1005	314	36
PE87FL1006	314	39
PE87FL1007	314	38
PE87FL1008	314	37
PE87FL1009	314	41
PE87FL1010	314	42
PE87FL1011	314	43
PE87FL1012	314	13
PE87FL1013	314	20
PE87FL1014	315	60
PE87FL1015	315	61
PE87FL1016	315	62
PE87FL1017	315	63
PE87FL1018	315	49
PE87FL1019	315	50
PE88D1000	315	90
PE88D1001	315	72
PE88D1002	315	81
PE88D12000	315	72
PE88D15000	315	66
PE88D16000	315	83
PE88D20000	315	73
PE88D20001	315	82
PE88D2001	315	86
PE88D2002	315	78
PE88D24000	315	68
PE88D25000	315	65
PE88D3000	315	64
PE88D32000	315	84
PE88D4000	315	87
PE88D40000	315	69
PE88D4001	315	88
PE88D4002	315	79
PE88D4003	315	71
PE88D5000	315	85
PE88D5001	315	74
PE88D6000	315	75
PE88D7000	315	76
PE88D8000	Web	
PE88D8001	315	89
PE88D8002	315	80
PE88D8003	315	67
PE88D9000	315	77
PE88X2000	317	47
PE88X2001	317	48
PE88X2002	317	49
PE88X2003	317	46
PE88X2010	317	50
PE88X2011	317	51
PE88X2012	318	52
PE88X2013	318	54
PE88X2014	318	56
PE88X2015	317	40
PE88X2016	317	41
PE88X2017	317	42
PE88X2018	317	43
PE88X2019	317	44
PE88X2020	317	45
PE88X2021	388	2
PE88X2022	388	1
PE88X2023	388	99
PE88X2024	388	97
PE88X2025	388	98
PE88X2026	388	96
PE8DP1001	312	
PE9000	26	E4
PE9001	26	A6
PE9002	31	E7
PE9003	26	C6
PE9005	33	A1
PE9006	31	D2
PE9007	30	C5
PE9008	49	C2
PE9009	49	B2
PE9011	26	D7
PE9013	49	B3
PE9014	36	B1
PE9015	27	A4
PE9063	32	E3
PE9064	29	D6
PE9065	29	B7
PE9066	36	C2
PE9067	35	B5
PE9068	35	E6
PE9070	36	B6
PE9072	38	D5
PE9073	36	D6
PE9074	38	A6
PE9075	38	B1
PE9076	40	B4
PE9077	38	D1
PE9078	40	D4
PE9079	37	B3
PE9080	39	C3
PE9081	37	E3
PE9082	39	C4
PE9083	26	B6
PE9084	26	C5
PE9085	31	B1
PE9086	27	E2
PE9087	44	C5
PE9088	33	D6
PE9089	32	A6
PE9090	43	A7
PE9091	26	E6
PE9093	Web	
PE9094	45	B5
PE9095	45	C1
PE9097	45	B1
PE9098	44	A3
PE9099	44	A2
PE9100	31	D3
PE9101	31	A2
PE9102	35	C3
PE9103	39	B5
PE9104	37	C4
PE9105	36	E7
PE9106	26	B7
PE9108	42	E5
PE9109	27	B1
PE9111	32	E6
PE9112	34	B1
PE9113	32	D6
PE9114	45	C5
PE9115	Web	
PE9116	41	E7
PE9117	42	A3
PE9118	41	E6
PE9119	42	C3
PE9120	41	B7
PE9122	42	B1
PE9123	33	D1
PE9125	32	A3
PE9126	28	C5
PE9127	31	B7
PE9128	31	A4
PE9129	28	C6
PE9130	33	B5
PE9131	33	E5
PE9132	42	B2
PE9135	42	D1
PE9136	42	C2
PE9137	42	E1
PE9138	42	C5
PE9139	42	D4
PE9140	42	D5
PE9141	42	E4
PE9142	39	B6
PE9143	39	C6
PE9144	37	B5
PE9145	37	C5
PE9146	39	D6
PE9147	39	E6
PE9148	37	D5
PE9149	37	E5
PE9150	27	D1
PE9151	27	C3
PE9152	27	C1
PE9153	27	D3
PE9154	44	E3
PE9155	32	B2
PE9158	27	E3
PE9160	46	C3
PE9163	46	B6
PE9164	46	A4
PE9165	45	B6
PE9166	Web	
PE9167	45	B7
PE9168	49	E2
PE9171	27	A2
PE9172	26	A7
PE9173	31	D4
PE9174	26	D5
PE9175	49	E1
PE9180	32	E7
PE9181	29	A1
PE9182	35	D6
PE9183	33	A5
PE9184	36	B2
PE9184NH	36	A3
PE9185	38	C6
PE9186	27	C6
PE9187	37	D7
PE9188	40	B3
PE9189	43	A3
PE9191	43	A4
PE9192	43	E2
PE9193	28	E4
PE9194	33	D3
PE9195	44	C2
PE9196	32	B4
PE9198	30	A6
PE9199	49	B1
PE9200	Web	
PE9201	45	E5
PE9204	27	B3
PE9205	28	E3
PE9206	33	E1
PE9207	27	E5
PE9208	27	A6
PE9209	45	A5
PE9210	28	B3
PE9211	29	A4
PE9212	28	D6
PE9213	43	C3
PE9214	38	D4
PE9215	36	A4
PE9216	32	C7
PE9217	31	B6
PE9218	44	E7
PE9219	44	A5
PE9220	23	D2
PE9221	23	C2
PE9222	Web	
PE9223	28	D2
PE9224	Web	
PE9225	34	E5
PE9226	44	C7
PE9227	48	C3
PE9228	48	D3
PE9229	48	D2
PE9230	27	B2
PE9231	27	B4
PE9232	48	B2
PE9234	27	C2
PE9235	48	A4
PE9236	27	C4
PE9237	33	B4
PE9238	33	C2
PE9239	32	A2
PE9240	42	D2
PE9241	42	A2
PE9242	42	E3
PE9243	41	D7
PE9244	48	B3
PE9245	48	D1
PE9246	36	A1
PE9247	35	D5
PE9248	48	A2
PE9249	34	D7
PE9251	40	A5
PE9252	39	E4
PE9253	38	E7
PE9255	39	A1
PE9256	36	E7
PE9257	32	D2
PE9258	33	C3
PE9259	36	C7
PE9260	38	D7
PE9261	33	B2
PE9263	33	A7
PE9264	28	B6
PE9265	29	B5
PE9266	29	E3
PE9267	29	B4
PE9268	29	C4
PE9269	26	B5
PE9270	44	C1
PE9271	48	C1
PE9272	Web	
PE9275	39	A4
PE9276	40	B5
PE9277	33	B5
PE9278	32	B1
PE9280	48	D7
PE9281	42	A5
PE9282	42	A6
PE9283	42	B6
PE9284	42	B5
PE9285	28	B2
PE9286	28	A2
PE9287	44	D4
PE9288	44	A4
PE9290	44	B2
PE9291	44	D7
PE9292	33	C5
PE9293	27	D5
PE9294	27	B6
PE9295	33	E2
PE9296	28	E5
PE9297	29	D3
PE9298	33	C4
PE9299	32	B3
PE9300	27	C5
PE9301	28	E2
PE9302	42	A1
PE9303	42	D3
PE9304	42	A4
PE9305	42	B3
PE9306	47	B2
PE9307	47	A2
PE9308	47	D1
PE9309	41	C7
PE9310	41	A7
PE9311	30	C7
PE9312	36	D2
PE9313	32	A5
PE9314	32	E4
PE9315	33	A6
PE9316	33	E5
PE9317	32	C5
PE9318	32	B5
PE9319

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE9438	20	D6
PE9439	38	C1
PE9440	40	C4
PE9441	Web	
PE9442	40	E4
PE9443	44	D1
PE9444	Web	
PE9445	43	B7
PE9446	32	E5
PE9448	Web	
PE9449	33	C7
PE9450	34	A1
PE9451	19	C4
PE9452	19	D4
PE9453	19	A5
PE9454	21	E4
PE9455	21	E1
PE9456	21	B5
PE9457	21	C1
PE9458	Web	
PE9459	Web	
PE9460	21	A3
PE9461	21	B6
PE9462	33	E4
PE9463	33	D4
PE9464	32	D3
PE9465	32	C3
PE9466	29	A3
PE9467	29	D2
PE9468	29	E2
PE9469	29	C2
PE9470	39	C1
PE9471	39	B1
PE9472	37	B1
PE9473	37	A1
PE9474	29	A2
PE9475	39	A3
PE9476	37	E2
PE9477	39	B3
PE9478	37	A3
PE9479	29	D1
PE9480	30	E1
PE9481	31	C1
PE9482	33	E7
PE9484	26	E5
PE9485	35	E7
PE9486	39	A5
PE9487	37	B4
PE9488	37	E4
PE9489	31	C7
PE9490	33	B1
PE9491	32	A1
PE9492	33	A2
PE9493	36	C6
PE9494	38	E5
PE9495	36	E6
PE9496	38	B6
PE9497	37	D4
PE9498	39	C5
PE9499	37	D3
PE9500	31	D5
PE9501	19	C7
PE9502	20	B2
PE9503	20	A2
PE9504	19	B7
PE9505	35	D1
PE9506	35	D3
PE9507	Web	
PE9508	36	D1
PE9511	37	E6
PE9512	40	A1
PE9513	37	C7
PE9516	30	C3
PE9517	30	D2
PE9518	30	B3
PE9519	Web	
PE9520	29	B3
PE9521	45	C2
PE9522	30	B2
PE9523	30	A2
PE9524	29	E1
PE9525	30	A3
PE9526	30	E3
PE9527	30	E2
PE9528	30	D3
PE9529	27	A5
PE9530	27	E4
PE9531	45	E3
PE9532	45	D3
PE9533	40	A7
PE9534	40	D6
PE9535	31	D6
PE9536	27	A1
PE9537	27	A3
PE9538	32	D1
PE9539	33	A3
PE9540	33	D2
PE9541	31	C4
PE9542	44	A7
PE9543	44	E6
PE9544	45	B2
PE9545	45	A2
PE9546	35	E3
PE9547	30	E7
PE9548	31	E3
PE9550	32	B6
PE9551	39	E3
PE9552	33	D7
PE9553	33	A4
PE9554	32	E2
PE9555	Web	
PE9556	24	D6
PE9557	24	D5
PE9558	25	E2
PE9559	25	D6
PE9560	43	C7
PE9561	44	E1
PE9562	44	D6
PE9563	44	D5
PE9564	45	D1
PE9565	31	D7
PE9566	33	C1
PE9567	28	B5
PE9568	34	D6
PE9569	28	B7
PE9570	32	A4
PE9571	34	E6
PE9572	Web	
PE9573	34	B6
PE9574	28	D4
PE9575	28	B4
PE9576	28	D3
PE9577	28	C3
PE9578	28	A4
PE9579	28	D5
PE9580	28	C4
PE9581	41	B3
PE9582	47	C4
PE9583	47	E6
PE9584	47	B4
PE9585	47	D6
PE9586	47	D4
PE9587	47	B7
PE9588	Web	
PE9589	47	A7
PE9593	41	C2
PE9594	41	E1
PE9595	31	D1
PE9596	41	C4
PE9597	41	B4
PE9598	41	E4
PE9599	41	A5
PE9600	41	C3
PE9602	41	D3
PE9603	41	E3
PE9604	41	C5
PE9605	41	B5
PE9606	41	E5
PE9607	41	D5
PE9608	46	A7
PE9609	46	D6
PE9610	46	E6
PE9611	46	B7
PE9612	47	E3
PE9613	47	B6
PE9614	47	A4
PE9615	47	C6
PE9616	46	D7
PE9617	46	E7
PE9618	47	A1
PE9619	47	B1
PE9620	36	E1
PE9621	35	E5
PE9622	48	D4
PE9623	48	C4
PE9624	48	A5
PE9625	48	E4
PE9626	47	E4
PE9627	47	A5
PE9628	47	C7
PE9629	47	D7
PE9630	48	A6
PE9631	48	C5
PE9632	46	C5
PE9633	46	B5
PE9634	46	A6
PE9635	Web	
PE9636	44	B5
PE9640	19	C5
PE9642	35	E2
PE9644	Web	
PE9647	20	A7
PE9648	20	B7
PE9649	22	C4
PE9650	22	E5
PE9651	22	E4
PE9652	22	B6
PE9653	36	E4
PE9654	36	A5
PE9655	38	C3
PE9656	38	D3
PE9658	22	A5
PE9659	22	D6
PE9660	21	D5
PE9661	21	E3
PE9662	21	A4
PE9663	21	A7
PE9664	21	B7
PE9665	21	B4
PE9666	21	A1
PE9667	20	E7
PE9668	Web	
PE9669	35	A3
PE9670	36	E2
PE9672	19	A6
PE9673	19	D7
PE9674	19	C6
PE9675	Web	
PE9676	Web	
PE9678	22	B3
PE9680	48	A1
PE9682	41	B6
PE9683	41	C6
PE9684	39	D3
PE9686	43	C2
PE9687	27	A7
PE9688	27	E6
PE9689	27	B7
PE9690	36	B4
PE9691	38	D2
PE9692	36	A4
PE9693	38	E2
PE9694	35	A4
PE9695	35	B7
PE9696	27	D7
PE9697	28	A1
PE9698	28	B1
PE9699	44	A6
PE9700	44	B6
PE9701	45	C6
PE9703	38	B7
PE9704	32	C2
PE9705	29	D7
PE9706	29	E7
PE9707	36	B7
PE9708	38	C7
PE9709	30	A1
PE9710	30	C1
PE9711	28	C1
PE9712	28	D1
PE9713	44	C6
PE9714	45	E1
PE9715	18	E6
PE9716	18	B6
PE9718	19	C2
PE9719	19	D2
PE9720	19	E3
PE9721	19	A4
PE9722	36	D5
PE9723	Web	
PE9724	38	B4
PE9725	38	C4
PE9726	38	A3
PE9727	36	C4
PE9728	36	D4
PE9729	38	B3
PE9730	34	A3
PE9731	34	B3
PE9732	41	A4
PE9733	41	D4
PE9734	46	C4
PE9735	48	E2
PE9736	48	C2
PE9737	Web	
PE9738	47	C3
PE9739	47	E5
PE9740	47	A6
PE9741	46	D5
PE9742	46	E4
PE9743	46	A5
PE9744	46	E5
PE9745	22	A4
PE9746	22	E3
PE9747	19	B2
PE9748	22	D5
PE9749	34	B7
PE9750	26	B2
PE9751	26	D1
PE9752	26	C2
PE9753	26	E1
PE9754	26	D2
PE9755	26	A2
PE9756	26	A1
PE9757	26	B1
PE9758	26	A5
PE9759	46	D3
PE9760	46	B3
PE9768	21	D7
PE9770	34	C2
PE9771	34	B2
PE9773	34	D2
PE9774	35	B4
PE9775	42	E7
PE9776	42	E6
PE9777	43	A1
PE9778	40	B1
PE9779	40	A3
PE9780	29	E5
PE9781	Web	
PE9782	21	E6
PE9783	44	D5
PE9786	39	A6
PE9787	Web	
PE9791	46	B2
PE9792	20	A5
PE9793	20	B5
PE9794	34	D1
PE9795	34	E1
PE9796	32	A7
PE9797	32	B7
PE9798	24	E7
PE9799	25	A1
PE9801	374	74
PE9802	374	84
PE9803	373	33
PE9804	373	60
PE9805	374	82
PE9806	373	39
PE9809	373	34
PE9810	374	76
PE9811	374	83
PE9812	373	23
PE9813A	373	22
PE9819	373	50
PE9820	374	2
PE9821	374	26
PE9822	374	38
PE9823	375	44
PE9824	375	53
PE9826	373	6
PE9827	373	11
PE9828	373	27
PE9830	374	9
PE9831	374	27
PE9832	375	39
PE9833	375	45
PE9834	375	50
PE9835	375	61
PE9837	374	1
PE9838	374	21
PE9839	374	28
PE9840	375	40
PE9842	375	63
PE9843	375	62
PE9846	373	42
PE9847	373	52
PE9848	374	77
PE9850	Web	
PE9850B/2F-10	364	1
PE9850B-10	368	90
PE9850-10	Web	
PE9850-15	368	92
PE9850-20	Web	
PE9850B/2F-15	364	5
PE9850B-15	368	93
PE9850B/2F-20	364	7
PE9850B-20	368	95
PE9851	Web	
PE9851-10	Web	
PE9851A-15	Web	
PE9851A-20	Web	
PE9851B/2F-10	364	10
PE9851B-10	368	97
PE9851B/2F-15	364	12
PE9851B-15	368	99
PE9851B/2F-20	364	14
PE9851B-20	368	2
PE9852	Web	
PE9852-10	Web	
PE9852-20	Web	
PE9852A-15	Web	
PE9852B/2F-10	364	19
PE9852B-10	368	4
PE9852B/2F-15	364	20
PE9852B-15	368	6
PE9852B/2F-20	364	24
PE9852B-20	368	8
PE9853	Web	
PE9853-10	Web	
PE9853-15	Web	
PE9853A-20	Web	
PE9853B/SF-10	364	28
PE9853B-10	368	11
PE9853B/SF-15	364	30
PE9853B-15	368	13
PE9853B/SF-20	364	32
PE9853B-20	368	15
PE9854	Web	
PE9854-10	Web	
PE9854-15	Web	
PE9854-20	Web	
PE9854B/SF-10	365	51
PE9854B-10	368	17
PE9854B/SF-15	364	40
PE9854B-15	368	19
PE9854B/SF-20	364	46
PE9854B-20	368	21
PE9854B/NF-10	365	50
PE9854B/NF-15	364	38
PE9854B/NF-20	364	44
PE9855	Web	
PE9855-10	Web	
PE9855-15	Web	
PE9855A-20	Web	
PE9855B/SF-10	365	54
PE9855B-10	368	23
PE9855B/SF-15	365	59
PE9855B-15	368	25
PE9855B/SF-20	365	66
PE9855B-20	368	27
PE9855B/NF-10	365	52
PE9855B/NF-15	365	57
PE9855B/NF-20	365	63
PE9856	Web	
PE9856-10	Web	
PE9856-15	Web	
PE9856-20	Web	
PE9856B/SF-10	365	70
PE9856B-10	368	28
PE9856B/SF-15	365	72
PE9856B-15	368	30
PE9856B/SF-20	365	76
PE9856B-20	368	32
PE9856B/NF-10	365	67
PE9856B/NF-15	365	71
PE9856B/NF-20	365	75
PE9857	Web	
PE9857-10	Web	
PE9857-15	Web	
PE9857-20	Web	
PE9857B/SF-10	365	80
PE9857B-10	368	35
PE9857B/SF-20	365	87
PE9857B-20	368	39
PE9857B/SF-15	365	84
PE9857B-15	368	37
PE9857B/NF-10	365	79
PE9857B/NF-15	365	83
PE9857B/NF-20	365	86
PE9858	Web	
PE9858-10	Web	
PE9858-15	Web	
PE9858A-20	Web	
PE9858B/SF-10	366	90
PE9858B-10	368	41
PE9858B/SF-15	366	93
PE9858B-15	368	43
PE9858B/SF-20	366	96
PE9858B-20	369	45
PE9858B/NF-10	366	89
PE9858B/NF-15	366	92
PE9858B/NF-20	366	95
PE9859	Web	
PE9859-10	Web	
PE9859-15	Web	
PE9859-20	Web	
PE9859B/SF-10	366	98
PE9859B-10	369	47
PE9859B/SF-15	366	1
PE9859B-15	369	49
PE9859B/SF-20	366	4
PE9859B-20	369	51
PE9859B/NF-10	366	97
PE9859B/NF-15	366	99
PE9859B/NF-20	366	3
PE9860	Web	
PE9860-10	Web	
PE9860-15	Web	
PE9860-20	Web	
PE9860B/SF-10	366	6
PE9860B-10	369	53
PE9860B/SF-15	366	8
PE9860B-15	369	55
PE9860B/SF-20	366	11
PE9860B-20	369	57
PE9860B/NF-10	366	5
PE9860B/NF-15	366	7
PE9860B/NF-20	366	10
PE9861	Web	
PE9861-10	Web	
PE9861-15	Web	
PE9861-20	Web	
PE9861B/SF-10	366	15
PE9861B-10	369	59
PE9861B/SF-15	366	19
PE9861B-15	369	61
PE9861B/SF-20	366	23
PE9861B-20	369	63
PE9861B/NF-10	366	13
PE9861B/NF-15	366	17
PE9861B/NF-20	366	21
PE9862	Web	
PE9862-10	Web	
PE9862-20	Web	
PE9862B/SF-10	366	27
PE9862B-10	369	65
PE9862B/SF-15	366	31
PE9862B-15	369	67
PE9862B/SF-20	367	35
PE9862B-20	369	69
PE9862B/NF-10	366	25
PE9862B/NF-15	366	29
PE9862B/NF-20	367	33
PE9863	Web	
PE9863-10	Web	
PE9863-20	Web	
PE9863B/SF-10	367	39
PE9863B-10	369	72
PE9863B-10-U	369	71
PE9863B/SF-15	367	43
PE9863B-15	369	75
PE9863B-15-U	369	74
PE9863B/SF-20	367	47
PE9863B-20	369	78
PE9863B-20-U	369	77
PE9863B/NF-10	367	37
PE9863B/NF-15	367	41
PE9863B/NF-20	367	45
PE9864	Web	
PE9864-10	Web	
PE9864-15	Web	
PE9864-20	Web	
PE9864B/SF-10	367	51
PE9864B-10	369	80
PE9864B/SF-15	367	55
PE9864B-15	369	82
PE9864B/SF-20	367	59
PE9864B-20	369	84
PE9864B/NF-10	367	50
PE9864B/NF-15	367	53
PE9864B/NF-20	367	57
PE9865	374	5
PE9866	373	40
PE9867	373	51
PE9868	373	58
PE9869	374	79
PE9870	374	3
PE9871	374	86
PE9872	375	60
PE9873	374	73
PE9874	373	49
PE9875	373	41
PE9876	374	20
PE9877	375	46
PE9878	373	21
PE9879	373	28
PE9881A-20	372	84
PE9881-24	368	84
PE9881-34	372	86
PE9881-42	372	83
PE9882	Web	
PE9883	Web	
PE9884	374	4
PE9887-11	372	81
PE9888-11	372	82
PE9889	374	75
PE9890	374	85
PE9909	Web	
PE9910	Web	
PE9911	Web	
PE9912	Web	
PE9913	Web	
PE9914	Web	
PE9915	Web	
PE9916	Web	
PE9917	Web	
PE9918	45	B4
PE9950	Web	
PE9951	Web	
PE9952	Web	
PE9953	Web	
PE9954	Web	
PE9955	Web	
PE9956	Web	
PE9957	Web	
PE9958	Web	
PE9959	Web	
PE9960	Web	
PE9961	Web	
PE9962	Web	
PE9963	Web	
PE9964	Web	
PE9965	Web	
PE9966	Web	
PE9967	Web	
PE9972	Web	
PE9973	20	A3
PE9974	20	B3
PE9975	22	C1
PE9976	23	A1
PE9977	22	B1
PE9978	20	C3
PE9979	22	D1
PE9980	23	B1
PE9981	22	E7
PE9982	20	E3
PE9983	22	E1
PE9984	20	A4
PE9985	20	D3
PE9986	22	A1
PE9987	23	C1
PE91002	38	A7
PE91003	36	A7
PE91004	Web	
PE91005	40	D5
PE91006	40	E5
PE91007	38	C2
PE91008	36	C5
PE91009	38	E3
PE91010	36	B5
PE91011	38	A4
PE91027	24	A5
PE91028	24	B5
PE91029	24	B6
PE91030	Web	
PE91031	32	D7
PE91032	31	E6
PE91033	Web	
PE91034	30	D5
PE91035	Web	
PE91036	38	A5
PE91038	24	E6
PE91039	24	C4
PE91040	30	E6
PE91041	Web	
PE91042	38	C5
PE91043	Web	
PE91044	27	D2
PE91045	38	E6
PE91046	43	D3
PE91048	20	C2
PE91049	Web	
PE91050	39	D7
PE91051	39	C2
PE91052	37	E1
PE91054	40	C1
PE91055	20	D2
PE91056	39	E7
PE91057	40	D1
PE91058	40	E1
PE91059	40	C2
PE91060	21	C7
PE91061	40	A2
PE91062	37	B7
PE91063	37	D6
PE91064	40	E2
PE91065	43	D1
PE91066	40	B2
PE91068	42	A7
PE91069	29	A6
PE91070	21	A2
PE91072	42	B7
PE91073	45	E2
PE91080	48	E5
PE91081	48	D5
PE91082	48	C6
PE91083	48	B6
PE91084	18	B7
PE91085	18	A6
PE91086	18	D6
PE91087	45	C4
PE91088	25	D1
PE91089	Web	
PE91090	25	C4
PE91091	25	A5
PE91092	23	D4
PE91093	23	B5
PE91094	23	E5
PE91095	23	C6
PE91098	42	C7
PE91101	42	D7
PE91102	42	D6
PE91103	37	B2
PE91104	26	E7
PE91105	49	A4
PE91106	49	D3
PE91107	49	E3
PE91108	18	B5
PE91109	18	D5
PE91111	20	B1
PE91113	Web	
PE91114	30	A7
PE91115	18	C7
PE91117	24	C5
PE91118	18	A5
PE91119	18	C5
PE91120	Web	
PE91121	19	A7
PE91122	20	B7
PE91123	20	E1
PE91124	21	B3
PE91125	21	C3
PE91126	21	D3
PE91127	21	C6
PE91128	21	D6
PE91129	39	A2
PE91134	31	A7
PE91135	35	C1
PE91136	Web	
PE91138	Web	
PE91140	31	E2
PE91141	31	A3
PE91144	22	B2
PE91145	20	C4
PE91146	20	D4
PE91147	23	A2
PE91148	23	E1
PE91149	Web	
PE91150	Web	
PE91151	35	D2
PE91152	Web	
PE91155	35	E4
PE91157	19	A1
PE91161	19	D1
PE91162	19	A3
PE91163	19	C3
PE91165	21	B2
PE91166	Web	
PE91167	21	E5
PE91168	21	D2
PE91169	22	D2
PE91170	Web	
PE91172	43	C6
PE91173	44	B1
PE91174	44	B3
PE91175	38	B5
PE91176	36	D3
PE91177	32	C4
PE91178	33	D5
PE91179	31	C5
PE91190	24	A4
PE91191	24	D4
PE91192	24	E5
PE91193	24	B7
PE91194	23	A3
PE91195	23	C3
PE91196	Web	
PE91197	23	E3
PE91198	30	B5
PE91199	30	C6
PE91200	31	B2
PE91201	31	A5
PE91202	43	D6
PE91203	43	D7
PE91204	44	D2
PE91205	44	B4
PE91206	25	B1
PE91207	25	E1
PE91208	25	D4
PE91209	25	A4
PE91210	Web	
PE91211	25	A3
PE91212	25	C3
PE91213	25	A7
PE91214	Web	
PE91215	25	C7
PE91216	23	C4
PE91217	23	E4
PE91218	23	A6
PE91219	23	C5
PE91220	Web	
PE91222	35	A5
PE91225	Web	
PE91227	24	B4
PE91228	24	E4
PE91229	24	A6
PE91230	24	C7
PE91231	23	B3
PE91232	Web	
PE91233	23	D3
PE91234	23	A4
PE91235	Web	
PE91236	30	D6
PE91237	31	C2
PE91238	31	B5
PE91239	43	E6
PE91240	43	E7
PE91241	44	E2
PE91242	44	C4
PE91243	25	C1
PE91244	25	A2
PE91245	25	E4
PE91246	25	B4
PE91247	25	B5
PE91248	25	B3
PE91249	25	D3
PE91250	25	B7
PE91251	25	E6
PE91252	25	D7
PE91253	Web	
PE91254	23	A5
PE91255	23	B6
PE91256	23	D5
PE91257	Web	
PE91258	36	C1
PE91259	40	B6
PE91260	40	B7
PE91261	41	A1
PE91262	41	A2
PE91263	40	E7
PE91264	40	E6
PE91265	40	C6
PE91266	40	C7
PE91267	40	D7
PE91268	41	C1
PE91269	41	E2
PE91270	41	D2
PE91290	36	B3
PE91291	22	A6
PE91292	Web	
PE91294	22	B4
PE91295	Web	
PE91298	21	B1
PE91299	39	D1
PE91300	39	E1
PE91301	39	B2
PE91302	37	C1
PE91303	37	D1
PE91304	37	A2
PE91305	39	A7
PE91306	39	B7
PE91307	39	C7
PE91308	40	D2
PE91309	37	A6
PE91310	37	B6
PE91311	37	C6
PE91312	37	A7
PE91321	35	B6
PE91324	46	D2
PE91327	Web	
PE91328	45	A6
PE91329	45	E6
PE91330	41	B1
PE91331	41	D1
PE91332	35	C5
PE91334	41	B2
PE91336	37	A5
PE91337	Web	
PE91339	32	D4
PE91341	34	D3
PE91342	34	E3
PE91343	34	A4
PE91344	34	C4
PE91345	34	D4
PE91346	34	E4
PE91347	34	A5
PE91348	46	A3
PE91349	46	E3
PE91350	31	A1
PE91360	37	C2
PE91361	39	D2
PE91362	37	D2
PE91363	39	E2
PE91364	43	C1
PE91370	30	B4
PE91371	30	C4
PE91372	30	D4
PE91373	30	A4
PE91380	40	E3
PE91381	44	C3
PE91385	23	A7
PE91386	24	A1
PE91387	23	D7
PE91388	31	C6
PE91389	24	D2
PE91390	25	D2
PE91391	25	E5
PE91392	45	A1
PE91393	36	A2
PE91395	26	A3
PE91396	26	C3
PE91397	Web	
PE91398	26	E3
PE91399	26	C4
PE91400	26	B4
PE91401	26	D3
PE91402	26	A4
PE91403	42	B4
PE91405	Web	
PE91406	Web	
PE91407	Web	
PE91408	Web	
PE91409	Web	
PE91410	Web	
PE91411	Web	
PE91412	Web	
PE91413	Web	
PE91414	Web	
PE91415	Web	
PE91416	Web	
PE91417	Web	
PE91418	Web	
PE91419	Web	
PE91420	Web	
PE91421	Web	
PE91422	Web	
PE91430	44	D3
PE91432	43	A6
PE91433	40	A4
PE91434	43	E5
PE91436	43	D5
PE91444	25	E3
PE91446	32	E1
PE91447	45	C7
PE91448	36	D7
PE91450	21	D1
PE91451	21	C4
PE91452	22	D4
PE91453	35	A6
PE91458	Web	
PE91459	19	B5
PE91461	18	C4
PE91462	18	B4
PE91463	18	D4
PE91464	23	E7
PE91465	23	B7
PE91466	23	E6
PE91467	23	C7
PE91468	25	B2
PE91469	25	C2
PE91470	25	C5
PE91471	25	A6
PE91472	25	D5
PE91473	25	B6
PE91474	24	E1
PE91475	24	C3
PE91476	24	C1
PE91477	24	A2
PE91478	24	B2
PE91479	24	A3
PE91480	24	D1
PE91481	24	B3
PE91482	24	D3
PE91483	24	C2
PE91484	24	E2
PE91487	45	E4
PE91492	35	C4
PE91493	35	D4
PE91494	35	C7
PE91495	35	D7
PE91496	35	E1
PE91497	35	A2
PE91498	19	E4
PE91499	21	A5
PE91502	20	B6
PE91504	35	C6
PE91505	44	A1
PE91506	33	E6
PE91507	38	E1
PE91508	19	D6
PE91510	20	C6
PE91511	19	C1
PE91512	19	B3
PE91513	19	D3
PE91514	21	E2
PE91515	22	E2
PE91516	20	E5
PE91517	20	E6
PE91518	19	B1
PE91519	19	E1
PE91520	21	C5
PE91521	21	A6
PE91522	21	C2
PE91523	22	A3
PE91525	20	C1
PE91526	20	A1
PE91527	19	A2
PE91528	22	C3
PE91529	19	D5
PE91530	31	B3
PE91531	30	B7
PE91532	30	E5
PE91534	19	E2
PE91535	35	B3
PE91536	36	E5
PE91537	32	C6
PE91538	20	C7
PE91540	19	B6
PE

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PETP1003	346	77
PETP1004	346	79
PETP1005	346	80
PETP1006	346	82
PETP1007	346	83
PETP1008	346	84
PETP1009	346	85
PETP1010	346	87
PETP1011	346	89
PETP1012	346	93
PETP1013	346	94
PETP1014	346	96
PETP1015	346	97
PETP1016	346	99
PETP1017	346	1
PEW05S0000-1	391	66
PEW05S0000-12	391	70
PEW05S0000-3	391	67
PEW05S0000-6	391	68
PEW05S0000-9	391	69
PEW06S0000-1	391	71
PEW06S0000-12	391	75
PEW06S0000-3	391	72
PEW06S0000-6	391	73
PEW06S0000-9	391	74
PEW08S0000-1	391	76
PEW08S0000-12	391	80
PEW08S0000-3	391	77
PEW08S0000-6	391	78
PEW08S0000-9	391	79
PEW10CP010-20	378	80
PEW10FS2	396	29
PEW10S010-3	391	81
PEW10S010-6	391	82
PEW10SP4	397	47
PEW10TR0001	393	64
PEW112FS5	397	40
PEW112SP5	397	58
PEW12FS2	396	30
PEW12S010-3	391	83
PEW12S010-9	391	84
PEW12SP4	397	48
PEW12TW001	395	67
PEW137FS7	397	41
PEW137RJ0001	391	63
PEW137SP7	397	59
PEW159FS7	397	42
PEW159SP7	397	60
PEW15A001	372	85
PEW15FS2	396	31
PEW15S010-12	391	87
PEW15SP4	397	49
PEW15TR0001	393	67
PEW187FS7	397	43
PEW187RJ0001	391	65
PEW187RJ0002	391	64
PEW187SP7	397	61
PEW19FS3	396	32
PEW19S010-12	391	91
PEW19S010-3	391	92
PEW19SP4	397	50
PEW19TR0001	393	68
PEW22B100	376	9
PEW22B101	376	10
PEW22CA100	372	97
PEW22CP010-20	379	93
PEW22ES3	396	33
PEW22S010-3	391	98
PEW22SP4	397	51
PEW22TW001	395	77
PEW284FS8	397	44
PEW284SP8	397	62
PEW28CP010-20	379	97
PEW28FS3	396	34
PEW28RJ0001	391	53
PEW28S010-3	392	5
PEW28S010-6	392	6
PEW28SP4	397	52
PEW28TW001	395	81
PEW340FS10	397	45
PEW340SP10	397	63
PEW34FS4	396	35
PEW34RJ0001	391	54
PEW34SP4	397	53
PEW42B100	377	14
PEW42B101	377	15
PEW42FS4	396	36
PEW42SP4	397	54
PEW430FS10	397	46
PEW430SP10	397	64
PEW5B0000	376	95
PEW5B0001	376	96
PEW5TW0000	394	53
PEW5TW0001	394	52
PEW5TW0002	394	54
PEW62FS5	397	37
PEW62RJ0001	391	56
PEW62RJ0002	391	55
PEW62SP5	397	55
PEW6B0000	376	97
PEW6B0001	376	98
PEW6TW0000	394	56
PEW6TW0001	394	55
PEW6TW0002	394	57
PEW75FS5	397	38
PEW75RJ0001	391	59
PEW75RJ0002	391	58
PEW75RJ0003	391	57
PEW75SP5	397	56
PEW8B0000	376	99
PEW8B0001	376	1
PEW8TW0000	394	59
PEW8TW0001	394	58
PEW8TW0002	394	60
PEW90FS5	397	39
PEW90RJ0001	391	62
PEW90RJ0002	391	60
PEW90RJ0003	391	61
PEW90SP5	397	57
PEWAD5000	377	39
PEWAD5001	377	40
PEWAD5002	377	41
PEWAD5003	377	42
PEWAD5004	377	44
PEWAD5005	377	46
PEWAD5006	377	49
PEWAD5007A	377	43
PEWAD5008	377	45
PEWAD5009	377	47
PEWAD5010	377	48
PEWAD5011	377	50
PEWAD5012	377	51
PEWAD5013	377	52
PEWAD5014	377	53
PEWAD5015	377	54
PEWAD5016	377	55
PEWAD5017	377	56
PEWAD5018	377	57
PEWAD5019	377	58
PEWAM0000	398	80
PEWAM0001	398	81
PEWAM0002	398	82
PEWAM0003	398	83
PEWAN028-10	368	91
PEWAN028-10KF	364	2
PEWAN028-10KM	364	3
PEWAN028-15	368	94
PEWAN028-15KF	364	4
PEWAN028-15KM	364	6
PEWAN028-20	368	96
PEWAN028-20KF	364	8
PEWAN028-20KM	364	9
PEWAN034-10	368	98
PEWAN034-10KF	364	11
PEWAN034-15	368	1
PEWAN034-15KF	364	13
PEWAN034-20	368	3
PEWAN034-20KF	364	15
PEWAN042-10	368	5
PEWAN042-10ELKF	364	16
PEWAN042-10KF	364	17
PEWAN042-10SF	364	18
PEWAN042-15	368	7
PEWAN042-15ELKF	364	21
PEWAN042-15KF	364	22
PEWAN042-15SF	364	23
PEWAN042-20	368	9
PEWAN042-20ELKF	364	25
PEWAN042-20KF	364	26
PEWAN042-20SF	364	27
PEWAN051-10	368	10
PEWAN051-10SF	364	29
PEWAN051-15	368	12
PEWAN051-15SF	364	31
PEWAN051-20	368	14
PEWAN051-20SF	364	33
PEWAN062-10	368	16
PEWAN062-10NF	364	34
PEWAN062-10ELSF	364	35
PEWAN062-10SF	364	36
PEWAN062-10SM	364	37
PEWAN062-15	368	18
PEWAN062-15NF	364	39
PEWAN062-15ELSF	364	41
PEWAN062-15SF	364	42
PEWAN062-15SM	364	43
PEWAN062-20	368	20
PEWAN062-20NF	364	45
PEWAN062-20ELSF	364	47
PEWAN062-20SF	364	48
PEWAN062-20SM	364	49
PEWAN075-10	368	22
PEWAN075-10NF	365	53
PEWAN075-10ELSF	365	55
PEWAN075-10SF	365	56
PEWAN075-15	368	24
PEWAN075-15NF	365	58
PEWAN075-15ELSF	365	60
PEWAN075-15SF	365	61
PEWAN075-20	368	26
PEWAN075-20NF	365	62
PEWAN075-20ELSF	365	64
PEWAN075-20SF	365	65
PEWAN090-10	368	29
PEWAN090-10ELSF	365	68
PEWAN090-10SF	365	69
PEWAN090-15	368	31
PEWAN090-15ELSF	365	73
PEWAN090-15SF	365	74
PEWAN090-20	368	33
PEWAN090-20ELSF	365	77
PEWAN090-20SF	365	78
PEWAN1005	368	86
PEWAN1006	368	87
PEWAN1007	368	88
PEWAN1008	368	89
PEWAN1009	367	81
PEWAN1010	367	82
PEWAN1011	367	83
PEWAN1012	368	85
PEWAN1013	367	77
PEWAN1014	367	78
PEWAN1015	367	79
PEWAN1016	367	80
PEWAN1017	367	73
PEWAN1018	367	74
PEWAN1019	367	75
PEWAN102-10	368	34
PEWAN102-10ELSF	365	81
PEWAN102-10SF	365	82
PEWAN102-15	368	36
PEWAN102-15SF	365	85
PEWAN102-20	368	38
PEWAN102-20SF	366	88
PEWAN1020	367	76
PEWAN1021	367	69
PEWAN1022	367	70
PEWAN1023	367	71
PEWAN1024	367	72
PEWAN1025	367	65
PEWAN1026	367	66
PEWAN1027	367	67
PEWAN1028	367	68
PEWAN1029	367	61
PEWAN1030	367	62
PEWAN1031	367	63
PEWAN1032	367	64
PEWAN1033	370	18
PEWAN1034	370	19
PEWAN1035	370	20
PEWAN1036	370	21
PEWAN1037	370	14
PEWAN1038	370	15
PEWAN1039	370	16
PEWAN1040	370	17
PEWAN1041	370	10
PEWAN1042	370	11
PEWAN1043	370	12
PEWAN1044	370	13
PEWAN1045	370	6
PEWAN1046	370	7
PEWAN1047	370	8
PEWAN1048	370	9
PEWAN1049	370	97
PEWAN1050	370	98
PEWAN1051	370	99
PEWAN1052	370	1
PEWAN1053	370	2
PEWAN1054	370	3
PEWAN1055	370	4
PEWAN1056	370	5
PEWAN1057	370	93
PEWAN1058	370	94
PEWAN1059	370	95
PEWAN1060	370	96
PEWAN1061	370	89
PEWAN1062	370	90
PEWAN1063	370	91
PEWAN1064	370	92
PEWAN1065	369	85
PEWAN1066	369	86
PEWAN1067	369	87
PEWAN1068	369	88
PEWAN1069	370	26
PEWAN1070	370	27
PEWAN1071	370	24
PEWAN1072	370	25
PEWAN1073	370	22
PEWAN1074	370	23
PEWAN1075	371	38
PEWAN1076	371	40
PEWAN1077	371	39
PEWAN1078	371	41
PEWAN1079	371	34
PEWAN1080	371	36
PEWAN1081	371	35
PEWAN1082	371	37
PEWAN1083	370	30
PEWAN1084	371	32
PEWAN1085	371	31
PEWAN1086	371	33
PEWAN1087	371	47
PEWAN1088	371	45
PEWAN1089	371	42
PEWAN1101	370	28
PEWAN1102	370	29
PEWAN1109	372	60
PEWAN1110	372	77
PEWAN1111	372	78
PEWAN1112	372	80
PEWAN1113	372	75
PEWAN1114	372	76
PEWAN1115	372	73
PEWAN1116	372	72
PEWAN1117	372	70
PEWAN1118	372	69
PEWAN1119	372	67
PEWAN112-10	368	40
PEWAN112-10SF	366	91
PEWAN112-15	368	42
PEWAN112-15ELSF	366	94
PEWAN112-20	368	44
PEWAN1120	372	66
PEWAN1121	372	63
PEWAN1122	372	62
PEWAN1123	372	61
PEWAN1124	371	49
PEWAN1125	371	50
PEWAN1126	371	51
PEWAN1127	371	52
PEWAN1128	371	53
PEWAN1129	371	54
PEWAN1130	371	55
PEWAN1131	371	57
PEWAN1132	371	58
PEWAN1133	371	48
PEWAN1134	371	46
PEWAN1135	371	43
PEWAN1136	371	44
PEWAN1137	372	64
PEWAN1138	372	68
PEWAN1139	372	71
PEWAN1140	372	74
PEWAN1141	372	65
PEWAN1142	372	79
PEWAN1143	371	59
PEWAN1144	371	58
PEWAN137-10	369	46
PEWAN137-15	369	48
PEWAN137-15SF	366	2
PEWAN137-20	369	50
PEWAN159-10	369	52
PEWAN159-15	369	54
PEWAN159-15SF	366	5
PEWAN159-20	366	56
PEWAN159-20SF	366	12
PEWAN187-10	369	58
PEWAN187-10NF	366	14
PEWAN187-10SF	366	16
PEWAN187-15	369	60
PEWAN187-15NF	366	18
PEWAN187-15SF	366	20
PEWAN187-20	369	62
PEWAN187-20NF	366	22
PEWAN187-20SF	366	24
PEWAN229-10	369	64
PEWAN229-10NF	366	26
PEWAN229-10SF	366	28
PEWAN229-15	369	66
PEWAN229-15NF	366	30
PEWAN229-15SF	367	32
PEWAN229-20	369	68
PEWAN229-20NF	367	34
PEWAN229-20SF	367	36
PEWAN284-10	369	70
PEWAN284-10NF	367	38
PEWAN284-10SF	367	40
PEWAN284-15	369	73
PEWAN284-15NF	367	42
PEWAN284-15SF	367	44
PEWAN284-20	369	76
PEWAN284-20NF	367	46
PEWAN284-20SF	367	48
PEWAN430-10	369	79
PEWAN430-10NF	367	49
PEWAN430-10SF	367	52
PEWAN430-15	369	81
PEWAN430-15NF	367	54
PEWAN430-15SF	367	56
PEWAN430-20	369	83
PEWAN430-20NF	367	58
PEWAN430-20SF	367	60
PEWAT1007-10	386	15
PEWAT1007-20	386	16
PEWAT1007-3	386	13
PEWAT1007-30	386	17
PEWAT1007-6	386	14
PEWAT1008-10	386	10
PEWAT1008-20	386	11
PEWAT1008-3	386	8
PEWAT1008-30	386	12
PEWAT1008-6	386	9
PEWAT1009-10	386	5
PEWAT1009-20	386	6
PEWAT1009-3	386	3
PEWAT1009-30	386	7
PEWAT1009-6	386	4
PEWAT1010-10	386	99
PEWAT1010-20	386	1
PEWAT1010-3	386	97
PEWAT1010-30	386	2
PEWAT1010-6	386	98
PEWAT1011-10	386	94
PEWAT1011-20	386	95
PEWAT1011-3	386	92
PEWAT1011-30	386	96
PEWAT1011-6	386	93
PEWAT1012-10	386	89
PEWAT1012-20	386	90
PEWAT1012-3	386	87
PEWAT1012-30	386	91
PEWAT1012-6	386	88
PEWCA1000	373	7
PEWCA1001	373	10
PEWCA1002A	373	25
PEWCA1003	373	36
PEWCA1004	373	46
PEWCA1005	373	44
PEWCA1006	374	72
PEWCA1007	373	66
PEWCA1008	374	71
PEWCA1009	373	63
PEWCA1010	374	99
PEWCA1011	374	94
PEWCA1012	374	98
PEWCA1013	374	92
PEWCA1014	374	17
PEWCA1015	374	14
PEWCA1016	374	16
PEWCA1017	374	12
PEWCA1018	373	19
PEWCA1019	373	17
PEWCA1020	373	2
PEWCA1021	373	9
PEWCA1022	373	16
PEWCA1023	373	32
PEWCA1024	373	43
PEWCA1025	373	59
PEWCA1026	373	18
PEWCA1027	373	26
PEWCA1028	373	35
PEWCA1029	373	45
PEWCA1030	374	69
PEWCA1031	373	68
PEWCA1032	373	62
PEWCA1033	373	61
PEWCA1034	373	67
PEWCA1035	373	64
PEWCA1036	373	65
PEWCA1037	374	78
PEWCA1038	374	80
PEWCA1039	374	81
PEWCA1040	374	97
PEWCA1041	374	96
PEWCA1042	374	91
PEWCA1043	374	90
PEWCA1044	374	95
PEWCA1045	374	93
PEWCA1046	374	19
PEWCA1047	374	11
PEWCA1048	374	10
PEWCA1049	374	15
PEWCA1050	374	13
PEWCA1051	374	23
PEWCA1052	374	22
PEWCA1053	374	25
PEWCA1054	374	24
PEWCA1055	374	37
PEWCA1056	374	35
PEWCA1057	374	36
PEWCA1058	374	34
PEWCA1059	374	33
PEWCA1060	373	20
PEWCA1061	373	38
PEWCA1062	375	42
PEWCA1063	375	52
PEWCA1064	375	49
PEWCA1065	375	51
PEWCA1066	375	56
PEWCA1067	375	57
PEWCA1068	375	58
PEWCA1069	375	59
PEWCA1070	373	37
PEWCA1071	373	38
PEWCA1072	373	47
PEWCA1073	373	48
PEWCA1074	373	47
PEWCA1075	374	70
PEWCA1076	374	33
PEWCA1077	375	55
PEWCA1078	373	99
PEWCA1079	375	63
PEWCA1080	375	64
PEWCA1081	375	47
PEWCA1082	375	48
PEWCA1083	374	31
PEWCA1084	374	30
PEWCA1085	374	29
PEWCA1086	374	7
PEWCA1087	374	6
PEWCA1088	374	8
PEWCA1089	374	87
PEWCA1090	374	88
PEWCA1092	373	55
PEWCA1093	373	56
PEWCA1095	373	53
PEWCA1096	373	54
PEWCA1097	373	29
PEWCA1098	373	30
PEWCA1099	373	24
PEWCA1100	373	13
PEWCA1101	373	12
PEWCA1102	373	8
PEWCA1103	373	1
PEWCA1104	373	4
PEWCA1105	374	32
PEWCA1106	374	89
PEWCA1107	373	57
PEWCA1108	373	31
PEWCA1109	373	5
PEWCA1110	372	98
PEWCA1111	375	67
PEWCA1112	375	69
PEWCA1113	375	71
PEWCA1114	375	73
PEWCA1115	375	66
PEWCA1116	375	68
PEWCA1117	375	70
PEWCA1118	375	72
PEWCA1119	374	74
PEWCA1120	375	65
PEWCP1005	379	4
PEWCP1006	379	2
PEWCP1007	379	3
PEWCP1008	379	8
PEWCP1009	379	9
PEWCP1010	379	10
PEWCP1011	379	11
PEWCP1012	379	12
PEWCP1013	379	13
PEWCP1014	379	14
PEWCP1015	379	15
PEWCP1016	379	16
PEWCP1017	379	18
PEWCP1018	379	20
PEWCP1019	379	22
PEWCP1020	379	17
PEWCP1021	379	19
PEWCP1022	379	21
PEWCP1023A	379	24
PEWCP1024	379	26
PEWCP1025	379	28
PEWCP1026	379	23
PEWCP1027	379	25
PEWCP1028	379	27
PEWCP1029	379	30
PEWCP1030	379	32
PEWCP1031	379	34
PEWCP1032	379	29
PEWCP1033	379	31
PEWCP1034	380	35
PEWCP1035	380	33
PEWCP1036	380	36
PEWCP1037	380	37
PEWCP1038	380	38
PEWCP1039	380	39
PEWCP1040	380	40
PEWCP1041	380	41
PEWCP1042	380	42
PEWCP1043	380	43
PEWCP1044	380	44
PEWCP1045	380	45
PEWCP1046	380	46
PEWCP1047	380	47
PEWCP1048	380	48
PEWCP1049	380	49
PEWCP1050	380	50
PEWCP1051	380	51
PEWCP1052A	380	52
PEWCP1053	380	53
PEWCP1054	380	54
PEWCP1055	380	55
PEWCP1056	380	58
PEWCP1057	380	60
PEWCP1058	380	62
PEWCP1059	380	56
PEWCP1060	380	57
PEWCP1061	380	59
PEWCP1062	380	61
PEWCP1063	380	64
PEWCP1064	380	66
PEWCP1065	380	68
PEWCP1066	380	70
PEWCP1067	380	63
PEWCP1068	380	65
PEWCP1069	380	67
PEWCP1070	380	69
PEWCP1071	380	72
PEWCP1072	380	74
PEWCP1073	380	76
PEWCP1074	380	78
PEWCP1075	380	71
PEWCP1076	380	73
PEWCP1077	380	75
PEWCP1078	380	77
PEWCP1079-10	379	95
PEWCP1080-20	379	85
PEWCR1000	378	64
PEWCR1001	378	63
PEWCR1002	378	62
PEWCR1003	378	61
PEWCR1004	378	60
PEWCR1005	378	59
PEWCT1000	381	79
PEWCT1001	381	80
PEWCT1002	381	81
PEWCT1003	381	82
PEWCT1004	381	83
PEWCT1005	381	84
PEWCT1006	381	85
PEWCT1007	381	86
PEWCT1008	381	87
PEWCT1009	381	88
PEWCT1010	381	89
PEWCT1011	381	90
PEWCT1012	381	91
PEWCT1013	381	92
PEWCT1014	381	93
PEWCT1015	381	94
PEWCT1016	381	95
PEWCT1017	381	96
PEWCT1018	381	97
PEWCT1019	381	98
PEWCT1020	381	99
PEWCT1021	381	3
PEWCT1022	381	5
PEWCT1023	381	7
PEWCT1024	381	1
PEWCT1025	381	2
PEWCT1026	381	4
PEWCT1027	381	6
PEWCT1028	381	9
PEWCT1029	381	11
PEWCT1030	381	13
PEWCT1032	381	8
PEWCT1033	381	10
PEWCT1034	381	12
PEWCT1035	381	14
PEWCT1036	381	17
PEWCT1037	381	19
PEWCT1038	381	21
PEWCT1039	381	23
PEWCT1040	381	16
PEWCT1041	381	18
PEWCT1042	381	20
PEWCT1043	381	22
PEWCT1044	382	24
PEWCT1045	382	25
PEWCT1046	382	26
PEWCT1047	382	27
PEWCT1048	382	28
PEWCT1049	382	29
PEWCT1050	382	30
PEWCT1051	382	31
PEWCT1052	382	32
PEWCT1053	382	33
PEWCT1054	382	34
PEWCT1055	382	35
PEWCT1056	382	36
PEWCT1057	382	37
PEWCT1058	382	38
PEWCT1059	382	39
PEWCT1060	382	40
PEWCT1061	382	42
PEWCT1062	382	44
PEWCT1063	382	46
PEWCT1064	382	41
PEWCT1065	382	43
PEWCT1066	382	45
PEWCT1067	382	47
PEWCT1068	382	48
PEWCT1069	382	54
PEWCT1070	382	58
PEWCT1071	382	62
PEWCT1072	382	50
PEWCT1073	382	52
PEWCT1074	382	56
PEWCT1075	382	60
PEWCT1076	382	49
PEWCT1077	382	55
PEWCT1078	382	59
PEWCT1079	382	63
PEWCT1080	382	51
PEWCT1085	382	53
PEWCT1086	382	57
PEWCT1087	382	61
PEWCT1088	382	66
PEWCT1089	382	70
PEWCT1090	382	74
PEWCT1091	382	76
PEWCT1092	382	67
PEWCT1093	382	71
PEWCT1094	382	75
PEWCT1095	382	79
PEWCT1096	382	65
PEWCT1097	382	69
PEWCT1098	382	73
PEWCT1099	382	77
PEWCT1100	382	82
PEWCT1101	383	86
PEWCT1102	383	90
PEWCT1103	383	94
PEWCT1104	382	80
PEWCT1105	382	84
PEWCT1106	383	88
PEWCT1107	383	92
PEWCT1108	382	83
PEWCT1109	383	87
PEWCT1110	383	91
PEWCT1111	383	95
PEWCT1112	382	81
PEWCT1113	382	85
PEWCT1114	383	89
PEWCT1115	383	93
PEWGA3201	389	24
PEWGA3202	389	22
PEWGA3203	389	21
PEWGA3204	389	20
PEWGA3205	389	19
PEWGA3206	389	18
PEWGA3208	389	23
PEWGA3210	395	98
PEWGA3211	395	97
PEWGA3212	395	96
PEWGA3213	395	95
PEWGA3214	395	94
PEWGA3215	395	93
PEWGHW1000	398	86
PEWGHW1001	398	85
PEWGHW9000	398	84
PEWGK1000	396	2
PEWGK1001	396	28
PEWGK1002	396	4
PEWGK1003	396	6
PEWGK1004	396	8
PEWGK1005	396	12
PEWGK1006	396	14
PEWGK1007	396	13
PEWGK1008	396	18
PEWGK1009	396	20
PEWGK1010	396	19
PEWGK1011	396	24
PEWGK1012	396	26
PEWGK1013	396	25
PEWGK1014	396	1
PEWGK1015	396	27
PEWGK1016	396	3
PEWGK1017	396	5
PEWGK1018	396	7
PEWGK1019	396	9
PEWGK1020	396	11
PEWGK1021	396	10
PEWGK1022	396	15
PEWGK1023	396	17
PEWGK1024	396	16
PEWGK1025	396	23
PEWGK1026	396	21
PEWGK1027	396	22
PEWGN1010	388	3
PEWGN1011	388	4
PEWGN1012	388	5
PEWGN1013	388	6
PEWGP1000	398	78
PEWGP1001	398	77
PEWGP1002	398	76
PEWGP1003	398	75
PEWGP1004	398	74
PEWGP1005	398	73
PEWGP1006	398	72
PEWGP1007	398	71
PEWGP1008	398	70
PEWGP1009	398	69
PEWGP1010	398	68
PEWGP1011	398	67
PEWGP1012	398	66
PEWGP1013	398	65
PEWGP1014	397	65
PEWGS6000	384	20
PEWGS6001	384	22
PEWGS6002	384	19
PEWGS6003	384	21
PEWGS6004	384	28
PEWGS6005	384	30
PEWGS6006	384	27
PEWGS6007	384	29
PEWGS6008	384	32
PEWGS6009	384	34
PEWGS6010	384	31
PEWGS6011	384	33
PEWGS6012	384	36
PEWGS6013	384	38
PEWGS6014	384	35
PEWGS6015	384	37
PEWGS6016	385	48
PEWGS6017	385	50
PEWGS6018	385	47
PEWGS6019	385	49
PEWGS6020	385	60
PEWGS6021	385

50-OHM CONVERSION TABLE
(dBm - volts- watts)

dBm	V	Po
+53	100.0	200W
+50	70.7	100W
+49	64.0	80W
+48	58.0	64W
+47	50.0	50W
+46	44.5	40W
+45	40.0	32W
+44	32.5	25W
+43	32.0	20W
+42	28.0	16W
+41	26.2	12.5W
+40	22.5	10W
+39	20.0	8W
+38	18.0	6.4W
+37	16.0	5W
+36	14.1	4W
+35	12.5	3.2W
+34	11.5	2.5W
+33	10.0	2W
+32	9.0	1.6W
+31	8.0	1.25W
+30	7.10	1.0W
+29	6.40	800 mW
+28	5.80	640 mW
+27	5.00	500 mW
+26	4.45	400 mW
+25	4.00	320 mW
+24	3.55	250 mW
+23	3.20	200 mW
+22	2.80	160 mW
+21	2.52	125 mW
+20	2.25	100 mW
+19	2.00	80 mW
+18	1.80	64 mW
+17	1.60	50 mW
+16	1.41	40 mW
+15	1.25	32 mW
+14	1.15	25 mW
+13	1.00	20 mW
+12	0.90	16 mW
+11	0.80	12.5 mW
+10	0.71	10 mW
+9	0.64	8 mW
+8	0.58	6.4 mW
+7	0.50	5 mW
+6	0.45	4 mW
+5	0.40	3.2 mW
+4	0.36	2.5 mW
+3	0.32	2.0 mW

dBm	V	Po
+2	0.28	1.6 mW
+1	0.25	1.25 mW
0	0.23	1.0 mW
-1	0.20	.80 mW
-2	0.18	.64 mW
-3	0.16	.50 mW
-4	0.14	.40 mW
-5	0.13	.32 mW
-6	0.12	.25 mW
-7	0.10	.20 mW
-8	0.09	.16 mW
-9	0.08	.125 mW
-10	0.07	.10 mW
-11	0.06	
-12	0.06	
-13	0.05	
-14	0.05	
-15	0.04	
-16	0.0355	
dBm	**mV**	**Po**
-17	31.5	
-18	28.5	
-19	25.1	
-20	22.5	.01 mW
-21	20.0	
-22	17.9	
-23	15.9	
-24	14.1	
-25	12.8	
-26	11.5	
-27	10.0	
-28	8.9	
-29	8.0	
-30	7.1	.001 mW
-31	6.25	
-32	5.8	
-33	5.0	
-34	4.5	
-35	4.0	
-36	3.5	
-37	3.2	
-38	2.85	
-39	2.5	
-40	2.25	.1 µW
-41	2.0	
-42	1.8	
-43	1.6	
-44	1.4	
-45	1.25	

dBm	mV	Po
-46	1.18	
-47	1.0	
-48	0.9	
-49	0.8	
-50	0.71	.01 µW
-51	0.64	
-52	0.57	
-53	0.5	
-54	0.45	
-55	0.4	
-56	0.351	
-57	0.32	
-58	0.286	
-59	0.251	
-60	0.225	.001 µW
-61	0.2	
-62	0.18	
-63	0.16	
-64	0.141	
dBm	**µV**	**Po**
-65	128	
-66	115	
-67	100	
-68	90	
-69	80	
-70	71	.1 nW
-71	65	
-72	58	
-73	50	
-74	45	
-75	40	
-76	35	
-77	32	
-78	29	
-79	25	
-80	22.5	.01 nW
-81	20	
-82	18	
-83	16	
-84	11.1	
-85	12.9	
-86	11.5	
-87	10.0	
-88	9.0	
-89	8.0	
-90	7.1	.001 nW
-91	6.1	
-92	5.75	
-93	5.0	

dBm	µV	Po
-94	4.5	
-95	4.0	
-96	3.51	
-97	3.2	
-98	2.9	
-99	2.51	
-100	2.25	.1 pW
-101	2.0	
-102	1.8	
-103	1.6	
-104	1.41	
-105	1.27	
-106	1.18	
dBm	**nV**	**Po**
-107	1000	
-108	900	
-109	800	
-110	710	.01 pW
-109	640	
-112	580	
-113	500	
-114	450	
-115	400	
-116	355	
-117	825	
-118	285	
-119	251	
-120	225	.001 pW
-121	200	
-122	180	
-123	160	
-124	141	
-125	128	
-126	117	
-127	100	
-128	90	
-129	80	
-130	71	.1 *f*W
-131	61	
-132	58	
-133	50	
-134	45	
-135	40	
-136	35	
-137	33	
-138	29	
-139	25	
-140	23	.01 *f*W

RETURN LOSS CONVERSION TABLE

Return Loss (dBm)	VSWR
46.064	1.01
40.086	1.02
36.607	1.03
34.151	1.04
32.256	1.05
30.714	1.06
29.417	1.07
28.299	1.08
27.318	1.09
26.444	1.10
25.658	1.11
24.943	1.12
24.289	1.13
23.686	1.14
23.127	1.15
22.607	1.16
22.120	1.17
21.664	1.18
21.234	1.19
20.828	1.20
20.443	1.21
20.079	1.22
19.732	1.23
19.401	1.24
19.085	1.25
18.783	1.26
18.493	1.27
18.216	1.28
17.949	1.29
17.690	1.30
17.445	1.31
17.207	1.32
16.977	1.33
16.755	1.34
16.540	1.35
16.332	1.36
16.131	1.37
15.936	1.38
15.747	1.39
15.563	1.40
15.385	1.41
15.211	1.42
15.043	1.43
14.879	1.44
14.719	1.45
14.564	1.46
14.412	1.47
14.264	1.48
14.120	1.49
13.979	1.50

Return Loss (dBm)	VSWR
13.842	1.51
13.708	1.52
13.577	1.53
13.449	1.54
13.324	1.55
13.201	1.56
13.081	1.57
12.964	1.58
12.849	1.59
12.736	1.60
12.625	1.61
12.518	1.62
12.412	1.63
12.308	1.64
12.207	1.65
12.107	1.66
12.009	1.67
11.913	1.68
11.818	1.69
11.725	1.70
11.634	1.71
11.545	1.72
11.457	1.73
11.370	1.74
11.285	1.75
11.202	1.76
11.120	1.77
11.039	1.78
10.960	1.79
10.881	1.80
10.804	1.81
10.729	1.82
10.654	1.83
10.581	1.84
10.509	1.85
10.437	1.86
10.367	1.87
10.298	1.88
10.230	1.89
10.163	1.90
10.097	1.91
10.032	1.92
9.968	1.93
9.904	1.94
9.842	1.95
9.780	1.96
9.720	1.97
9.660	1.98
9.601	1.99
9.542	2.00


Return Loss (dBm)	VSWR
9.485	2.01
9.428	2.02
9.372	2.03
9.317	2.04
9.262	2.05
9.208	2.06
9.155	2.07
9.103	2.08
9.051	2.09
8.999	2.10
8.949	2.11
8.899	2.12
8.849	2.13
8.800	2.14
8.752	2.15
8.705	2.16
8.657	2.17
8.611	2.18
8.565	2.19
8.519	2.20
8.474	2.21
8.430	2.22
8.386	2.23
8.342	2.24
8.299	2.25
8.257	2.26
8.215	2.27
8.173	2.28
8.138	2.29
8.091	2.30
8.051	2.31
8.011	2.32
7.972	2.33
7.933	2.34
7.894	2.35
7.856	2.36
7.818	2.37
7.781	2.38
7.744	2.39
7.707	2.40
7.671	2.41
7.635	2.42
7.599	2.43
7.564	2.44
7.529	2.45
7.494	2.46
7.460	2.47
7.426	2.48
7.393	2.49
7.360	2.50

Return Loss (dBm)	VSWR
7.327	2.51
7.294	2.52
7.262	2.53
7.230	2.54
7.198	2.55
7.167	2.56
7.135	2.57
7.105	2.58
7.074	2.59
7.044	2.60
7.014	2.61
6.984	2.62
6.954	2.63
6.925	2.64
6.896	2.65
6.867	2.66
6.839	2.67
6.811	2.68
6.783	2.69
6.755	2.70
6.728	2.71
6.700	2.72
6.673	2.73
6.646	2.74
6.620	2.75
6.594	2.76
6.567	2.77
6.541	2.78
6.516	2.79
6.490	2.80
6.465	2.81
6.440	2.82
6.415	2.83
6.390	2.84
6.366	2.85
6.341	2.86
6.317	2.87
6.293	2.88
6.270	2.89
6.246	2.90
6.223	2.91
6.200	2.92
6.177	2.93
6.154	2.94
6.131	2.95
6.109	2.96
6.086	2.97
6.064	2.98
6.042	2.99
6.021	3.00


Return Loss (dBm)	VSWR
5.999	3.01
5.970	3.02
5.956	3.03
5.935	3.04
5.914	3.05
5.893	3.06
5.872	3.07
5.852	3.08
5.832	3.09
5.811	3.10
5.791	3.11
5.771	3.12
5.751	3.13
5.732	3.14
5.712	3.15
5.693	3.16
5.674	3.17
5.654	3.18
5.635	3.19
5.617	3.20
5.598	3.21
5.579	3.22
5.561	3.23
5.542	3.24
5.524	3.25
5.506	3.26
5.488	3.27
5.470	3.28
5.452	3.29
5.435	3.30
5.417	3.31
5.400	3.32
5.383	3.33
5.365	3.34
5.348	3.35
5.331	3.36
5.315	3.37
5.298	3.38
5.281	3.39
5.265	3.40
5.248	3.41
5.232	3.42
5.216	3.43
5.200	3.44
5.184	3.45
5.168	3.46
5.152	3.47
5.137	3.48
5.121	3.49
5.105	3.50

Technical
www.pasternack.com
Same-Day Shipping.
866-727-8376


MOUNTING HOLES




CODE	A	B	C
A01	.500	.340	.102
A02	.687	.500	.109
A03	.687	.500	#3-56 TAP
A04	.687	.500	.125
A05	1.000	.718	.125
A06	.750	.531	.140
A07	.750	.531	.125
A08	1.190	.906	.125
A09	.687	.500	#4-40 TAP
A10	.687	.500	.136
A11	1.250	.975	.147
A12	2.000	1.440	.257
A13	1.000	.718	.141
A14	1.000	.718	.144
A15	.687	.500	.104
A16	.750	.531	.136
A17	.375	.232	.067
A18	.625	.437	.094
A19	1.000	.718	#6-32 TAP
A20	.500	.340	#2-56 TAP
A21	1.250	.975	.142
A22	.375	.232	.093




CODE	A
F01	.250
F02	.500
F03	.630
F04	1.200
F05	.380
F06	.450
F07	.200
F08	.362
F09	.220
F10	.317
F11	4.83mm
F12	.390




CODE	A	B
B01	.195	.177
B02	.250	.235
B03	.330	.295
B04	.380	.350
B05	.440	.410
B06	.512	.480
B07	.760	.720
B08	.565	.537
B09	.314	.296
B10	.140	.126
B11	.695	.655
B12	.625	.575
B13	.405	.361
B14	.277	.252
B15	.630	.596
B16	.317	.285
B17	.284	.268




CODE	A	B
J01	.200	.046




CODE	A	B	C
D01	.200	.067	.062
D02	.200	.067	.046
D03	.100	.031	.031
D04	.200	.052	.052
D05	.260	.067	.043
D06	.200	.052	.047
D07	.200	.055	.043
D08	.200	.067	.035
D09	.200	.055	.028
D10	.200	.055	.035
D11	.320	.091	.031
D12	.400	.062	.062
D13	.320	.091	.091
D14	.340	.091	.043
D15	.164	.067	.091
D16	.500	.126	.440
D17	.380	.083	.043




CODE	A	B	C
C01	.223	.481	.102
C02	.260	.481	.102
C03	.192	.328	.067
C04	.640	1.000	.125
C05	.275	.481	.102
C06	.230	.354	.067
C07	.188	.328	.093



CODE	A	B
G01	.640	.546
G02	.380	.340
G03	.765	.712
G04	.362	.323
G05	.236	.197
G06	.217	.177
G07	.380	.310
G08	1.161	1.000



CODE	A	B	C	D	E
E01	.375	.500	.340	.222	.093




CODE	A	B	C	D
H01	.687	.500	.125	.045

Appendix


CONNECTOR IDENTIFIER

SPECIFICATIONS SHOWN ARE INTENDED FOR IDENTIFICATION PURPOSES ONLY


1.0 / 2.3 SLIDE ON




1.0 / 2.3 SNAP ON




1.6 / 5.6




1.85 mm**




2.4 mm**




2.92 mm*




3.5 mm*




7 mm




7/16




3/4-20 TWINAX




10 - 32




BANANA




BNC



REVERSE POLARITY BNC



75 OHM BNC



*SMA, 2.92mm, & 3.5mm CONNECTORS WILL MATE MECHANICALLY & ELECTRICALLY TO EACH OTHER.

**1.85mm & 2.4mm CONNECTORS WILL MATE MECHANICALLY & ELECTRICALLY TO EACH OTHER.


Technical
www.pasternack.com
Same-Day Shipping.
866-727-8376

CONNECTOR IDENTIFIER


SPECIFICATIONS SHOWN ARE INTENDED FOR IDENTIFICATION PURPOSES ONLY

BNC TWINAX

PLUG




JACK




C

MALE




FEMALE




D SUBMINIATURE

PLUG




RECEPTACLE




F

MALE




FEMALE




FAKRA

PLUG



FAKRA

JACK




FAKRA

COMPLETE KEY CODE INFO


CODE	JACK	PLUG	COLOR	APPLICATION	CODE	JACK	PLUG	COLOR	APPLICATION
A			BLACK	RADIO WITH PHANTOM SUPPLY	H			VIOLET	GPS: TELEMATICS AND NAVIGATION
B			WHITE	RADIO WITHOUT PHANTOM SUPPLY	I			BEIGE	BLUETOOTH
C			BLUE	GPS: TELEMATICS OR NAVIGATION	K			CURRY	RADIO WITH I.F. OUTPUT (ANTENNA DIVERSITY)
D			BORDEAUX	GSM: CELLULAR PHONE	Z			WATER BLUE	NEUTRAL CODING

FME


PLUG



JACK




GR874




HN

MALE




FEMALE




LC

MALE




FEMALE




UMCX


PLUG



JACK




MC-CARD




MCX

PLUG



JACK




Appendix

CONNECTOR IDENTIFIER


SPECIFICATIONS SHOWN ARE INTENDED FOR IDENTIFICATION PURPOSES ONLY

REVERSE POLARITY MCX

PLUG




JACK




75 OHM MCX

PLUG




JACK




MHV

MALE




FEMALE




MINI 75 OHM SMB

PLUG




JACK




MINI SMP

MALE




FEMALE




MINI-UHF

MALE




FEMALE




MMCX

PLUG




JACK




N

MALE




FEMALE




REVERSE POLARITY N

MALE




FEMALE




75 OHM N

MALE




FEMALE




PAL


PLUG



JACK




POSITIVE SNAP




QMA

MALE




FEMALE




RCA

PLUG




JACK




SC

MALE



FEMALE



Appendix


Technical
www.pasternack.com
Same-Day Shipping.
866-727-8376

CONNECTOR IDENTIFIER


SPECIFICATIONS SHOWN ARE INTENDED FOR IDENTIFICATION PURPOSES ONLY

SHV

PLUG




JACK




SMA*

MALE




FEMALE




REVERSE POLARITY SMA

MALE




FEMALE




SMA REVERSE THREAD

MALE




FEMALE




SMB

PLUG




JACK




75 OHM SMB

PLUG




JACK




SMC

PLUG




JACK




75 OHM SMC

PLUG




JACK




SMP

MALE




FEMALE




SSMA

MALE




FEMALE




SSMB

PLUG




JACK




TNC

MALE




FEMALE




75 OHM TNC

MALE




FEMALE




REVERSE POLARITY TNC

MALE




FEMALE




UHF

MALE




FEMALE



*SMA, 2.92mm & 3.5mm CONNECTORS WILL MATE MECHANICALLY & ELECTRICALLY TO EACH OTHER.

CONNECTOR FREQUENCY RANGE CHART



Notes:

1: BNC-75 Ohm connectors operate up to 1 GHz
2: SMB-75 Ohm & Mini SMB-75 Ohm connectors operate up to 4 GHz
3: MCX-75 Ohm connectors operate up to 6 GHz
4: SMC-75 Ohm connectors operate up to 10 GHz
5: N-75 Ohm connectors operate up to 1.5 GHz
6: TNC-75 Ohm connectors operate up to 1 GHz

International Distribution Partners

AUSTRALIA
ROJONE PTY LTD.
TEL: +61 2 9829 1555
FAX: +61 2 9605 8812
EMAIL: sales@rojone.com.au
WEB: www.rojone.com.au

AUSTRIA
MRC GIGACOMP GMBH & CO. KG
TEL: +49 89 4161 5994 0
FAX: +49 89 4161 5994 5
EMAIL: info@mrc-gigacomp.com
WEB: www.mrc-gigacomp.com

BELGIUM
RIMARCK
TEL: +31 229 50 34 78
FAX: +31 229 50 34 79
EMAIL: info@rimarck.com
WEB: www.rimarck.com

BRAZIL
VERMONT REP COM LTDA
TEL: +55 11 3726 6655
EMAIL: vendas@vermont-rep.com
WEB: www.vermont-rep.com

CHINA PRC
PASTERNACK CHINA
TEL: +86 400 928 5100
EMAIL: sales@pasternack.cn
WEB: www.pasternack.cn

CZECH REPUBLIC
H TEST A.S.
TEL: +420 235 365 207
FAX: +420 235 363 893
EMAIL: info@htest.cz
WEB: www.htest.cz

DENMARK
AMERIKANSKA TELEPRODUKTER AB
TEL: +46 8 554 909 50
FAX: +46 8 554 909 51
EMAIL: info@amska.se
WEB: www.amska.se

FINLAND
AMERIKANSKA TELEPRODUKTER AB
TEL: +46 8 554 909 50
FAX: +46 8 554 909 51
EMAIL: info@amska.se
WEB: www.amska.se

FRANCE
EQUIPEMENTS SCIENTIFIQUES S.A.
TEL: +33 1 47 95 99 60
FAX: +33 1 47 01 16 22
EMAIL: hyper@es-france.com
WEB: www.es-france.com

GERMANY
MRC GIGACOMP GMBH & CO. KG
TEL: +49 89 4161 5994 0
FAX: +49 89 4161 5994 5
EMAIL: info@mrc-gigacomp.com
WEB: www.mrc-gigacomp.com

INDIA
SPUR MICROWAVE INC.
TEL: +91 80 252 003 83
FAX: +91 80 252 842 23
EMAIL: pe@spurindia.com
WEB: www.spurindia.com

INDONESIA
PRECISION TECHNOLOGIES PTE LTD.
TEL: +65 6273 4573
FAX: +65 6273 8898
EMAIL: precision@pretech.com.sg
WEB: www.pretech.com.sg

IRELAND
SPECTECH LIMITED
TEL: +44 0 1420 544789
FAX: +44 0 1420 544788
EMAIL: sales@spectechlimited.com
WEB: www.spectechlimited.com

ISRAEL
TRITECH LTD.
TEL: +972 73 2248800
FAX: +972 9 748 2616
EMAIL: RFsales@Tritech.co.il
WEB: www.tritech.co.il

ITALY
M.P.G. INSTRUMENTS S.R.L.
TEL: +39 06 4071603 (ROME)
EMAIL: mpgrm@mpginstruments.com
TEL: +39 02 99813130 (MILAN)
EMAIL: mpgmi@mpginstruments.com
WEB: www.mpginstruments.com

JAPAN
M-RF CO., LTD.
TEL: +81 3 5244 4890
FAX: +81 3 3258 2030
EMAIL: pasternack@mrf.co.jp
WEB: www.mrf.co.jp

KAZAKHSTAN
VILCOM HOLDING LLC
TEL: +7 495 961 34 43
FAX: +7 495 961 34 43
EMAIL: pasternack@vilcom.ru
WEB: www.pasternack.vilcom.ru

LUXEMBOURG
RIMARCK
TEL: +31 229 50 34 78
FAX: +31 229 50 34 79
EMAIL: info@rimarck.com
WEB: www.rimarck.com

MALAYSIA
PRECISION TECHNOLOGIES PTE LTD.
TEL: +65 6273 4573
FAX: +65 6273 8898
EMAIL: precision@pretech.com.sg
WEB: www.pretech.com.sg

NAMIBIA
RF DESIGN
TEL: +27 21 555-8400
EMAIL: sales@rfdesign.co.za
WEB: www.rfdesign.co.za

NETHERLANDS
RIMARCK
TEL: +31 229 50 34 78
FAX: +31 229 50 34 79
EMAIL: info@rimarck.com
WEB: www.rimarck.com

NEW ZEALAND
ROJONE PTY LTD.
TEL: +61 2 9829 1555
FAX: +61 2 9605 8812
EMAIL: sales@rojone.com.au
WEB: www.rojone.com.au

NORWAY
AMERIKANSKA TELEPRODUKTER AB
TEL: +46 8 554 909 50
FAX: +46 8 554 909 51
EMAIL: info@amska.se
WEB: www.amska.se

POLAND
ZEAP MERATRONIK S.A.
TEL: +48 22 855 34 32
FAX: +48 22 644 25 56
EMAIL: sales@meratronik.pl
WEB: www.meratronik.pl

PORTUGAL
ALTAIX ELECTRONICA, S.A.
TEL: +34 91 636 3939
FAX: +34 91 636 3909
EMAIL: pasternack@altaix.com
WEB: www.altaix.com

RUSSIA
VILCOM HOLDING LLC
TEL: +7 495 961 34 43
FAX: +7 495 961 34 43
EMAIL: pasternack@vilcom.ru
WEB: pasternack.vilcom.ru

SINGAPORE
PRECISION TECHNOLOGIES PTE LTD.
TEL: +65 6273 4573
FAX: +65 6273 8898
EMAIL: precision@pretech.com.sg
WEB: www.pretech.com.sg

SLOVAKIA
H TEST A.S.
TEL: +420 235 365 207
FAX: +420 235 363 893
EMAIL: info@htest.cz
WEB: www.htest.cz

SOUTH AFRICA
RF DESIGN
TEL: +27 21 555-8400
EMAIL: sales@rfdesign.co.za
WEB: www.rfdesign.co.za

SOUTH KOREA
Y C INTERNATIONAL CO., LTD.
TEL: +82 2 2157 2707
FAX: +82 2 2157 2709
EMAIL: yc@ycinternational.co.kr
WEB: www.ycinternational.co.kr

SPAIN
ALTAIX ELECTRONICA, S.A.
TEL: +34 91 636 3939
FAX: +34 91 636 3909
EMAIL: pasternack@altaix.com
WEB: www.altaix.com

SWEDEN
AMERIKANSKA TELEPRODUKTER AB
TEL: +46 8 554 909 50
FAX: +46 8 554 909 51
EMAIL: info@amska.se
WEB: www.amska.se

SWITZERLAND
GIGACOMP AG
TEL: +41 31 868 4455
FAX: +41 31 868 4450
EMAIL: info@gigacomp.ch
WEB: www.gigacomp.ch

THAILAND
PRECISION TECHNOLOGIES PTE LTD.
TEL: +65 6273 4573
FAX: +65 6273 8898
EMAIL: precision@pretech.com.sg
WEB: www.pretech.com.sg

TURKEY
SACA ELECTRONIK A S
TEL: +90 312 5575424 (ANKARA)
TEL: +90 216 5040787 (ISTANBUL)
EMAIL: info@saca.com.tr
WEB: www.saca.com.tr

UNITED KINGDOM
SPECTECH LIMITED
TEL: +44 0 1420 544789
FAX: +44 0 1420 544788
EMAIL: sales@spectechlimited.com
WEB: www.spectechlimited.com

© 2022 Infinite Electronics, Inc. Pasternack is a registered trademark of Infinite Electronics, Inc.

PASTERNACK®
an INFINITE brand







RF Solutions from RF Engineers

Same-Day Shipping
on orders placed by 4:00 pm PST

24-Hour Support
by phone, chat or email

Secure Online Ordering
pasternack.com
sales@pasternack.com

USA & Canada: 1 (866) 727-8376
International: +1 (949) 261-1920