PASTERNACK®
an INFINITE brand

Authorized Pasternack Distributor:

SPECTECH LIMITED
TEL: +44 0 1420 544789
FAX: +44 0 1420 544788
EMAIL: sales@spectechlimited.com
WEB: www.spectechlimited.com

2022
RF Product Guide

Same-Day Shipping | Largest Selection | Expert Technical Support

With Over 45 Years of RF Expertise, It's More Than Parts That Sets Us Apart

Since 1972, Pasternack has been satisfying the urgent requirements of engineers around the world by offering the largest in-stock, ready-to-ship selection of RF, microwave, and mmWave components, assemblies and devices, including over 40,000 popular and hard-to-find items across 107 categories of interconnect, passives, actives, antennas, and test and measurement. Ranging from DC to 220 GHz maximum frequency levels, Pasternack components are used in a wide range of test, development and deployment environments for military/aerospace, telecom, commercial, and industrial applications.

- 99.4% in-stock availability
- Same-day shipping
- No minimum order quantity
- 24/7 assistance by phone, email or chat
- Engineers on-hand to answer questions
- International distribution partner network

Largest RF Selection Available for Same-Day Shipping

- Adapters
- Amplifiers
- Antennas
- Attenuators/Equalizers
- Baluns
- Bias Tees/DC Blocks
- Cable Assemblies
- Cables
- Connectors
- Connector Accessories
- Couplers
- Educational Products
- Filters
- Frequency Multipliers/Dividers
- Impedance Matching
- Isolators/Circulators
- Limiters/Detectors
- Mixers/Modulators
- Noise Sources
- Oscillators/Synthesizers
- Phase Shifters/Trimmers
- Power Dividers/Combiners
- Rotary Joints
- Surge Protectors
- Switches
- Terminations
- Test and Measurement
- Tools
- Waveguides
- 60 GHz Systems & Modules

PASTERNACK
an INFINITE brand

Expanded Portfolio of High Frequency Components

In Stock and Available for Same-Day Shipping!

Pasternack's RF Engineering team has curated a broad portfolio of microwave and millimeter wave components to address the needs of 5G innovation and testing, along with other applications requiring higher frequencies and greater bandwidth. Whether your high frequency requirements are for active, passive, or interconnect products, Pasternack has you covered with the industry's largest in-stock selection available for same-day shipping.

Waveguide Components to 220 GHz

Electromechanical Switches to 50 GHz

Waveguide Electromechanical Switches to 40 GHz

Test Cables and Adapters 2.92mm/40 GHz, 2.4mm/50 GHz 1.85mm/70 GHz, 1.0mm/110 GHz

Broadband Amplifiers to 86.5 GHz



Mixers and Detectors to 110 GHz

PIN Diode Switches to 67 GHz

High Frequency Power Dividers/ Couplers to 67 GHz

Calibrated Noise Sources to 60 GHz

High Band 5G 28 GHz and 39 GHz

RF PRODUCT GUIDE INDEX

RF Loads with Frequencies up to 67 GHz; ProLine Series Standard Gain Waveguide Horn Antennas; High-Power RF and Microwave PIN Diode Coaxial Packaged Switches; Input Protected Low Noise Amplifiers; Coaxial Packaged Voltage Controlled Oscillators (VCO) Cover Broad Frequency Bands; Sub-6 GHz RF Antennas for 5G; etc.	3	NEW PRODUCT ADDITIONS
5G Solution from Pasternack	5	5G SOLUTIONS
Adapter Selection Guide; Adapter Locator (Part Number Identifier); Low PIM Adapters, Adapters to all Connectors	9	ADAPTERS
Amplifiers Selection Guide; Bi-Directional Amplifiers; Broadband Amplifiers; DC Coupled Amplifiers; Gain Block Amplifiers; Limiting Amplifiers; Linear Amplifiers; Log Amplifiers; Low Noise Amplifiers; Power-GaN Amplifiers; Rackmount Variable Gain Amplifiers; Amplifiers Accessories	49	AMPLIFIERS
Directional Antennas; Omni Directional Antennas; Antenna Mounts	60	ANTENNAS
Attenuators Selection Guide; Continuously Variable Attenuators; DC Bias Attenuators; Fixed Attenuators; Step Attenuators; TTL, CMOS, Relay and USB Attenuators; Voltage Variable Attenuators; Positive Slope Equalizers	68	ATTENUATORS & EQUALIZERS
Baluns	86	BALUNS
Bias Tees; DC Blocks	87	BIAS TEES & DC BLOCKS
Cable Assemblies Selection Guide; Cable Assemblies Locator (By Connector Type); High Reliability and Low PIM Cable Assemblies, Precision and Standard Cable Assemblies	88	CABLE ASSEMBLIES
Circulators; Isolators	222	CIRCULATORS & ISOLATORS
75 Ohm Broadcast; Communications; High Performance; RG MIL-C-17 Type Cables; Semi-Rigid & Formable; Twinax	225	COAX CABLES
Connector Selection Guide; Connector Locator (By Connector Type); All Connectors; Non-Shorting Caps; Shorting Caps	231	CONNECTORS
Dual Directional Couplers; Single Directional Couplers; 90 Degree and 180 Degrees Hybrids	302	COUPLERS & HYBRIDS
RF Diplexers	307	RF DIPLEXERS
Bandpass Filters; Highpass Filters; Lowpass Filters; Band Pass Filters; Band Reject Filters; Harmonic Filters	308	FILTERS
Mixers and Bi-Phase Modulators; Frequency Dividers; Frequency Multipliers	310	FREQ. CONVERSION COMPONENTS
Hi-REL Limiters; PIN-PIN Limiters; PIN-Schottky Limiters; Biased Detectors, Finline Detectors, Log Detectors; Phase Detectors, Power Detectors; Schottky Zero Bias Detectors; Threshold Detectors; Tunnel Diode Zero Bias Detectors	314	LIMITERS & DETECTORS
Precision and Standard Noise Sources	317	NOISE SOURCES
Adjustable Phase Shifters and Trimmers; 8 Bit Programmable Phase Shifters; Analog Phase Shifters	318	PHASE SHIFTERS/ TRIMMERS
Resistive and Reactive Power Dividers; Wilkinson Power Dividers; Broadband	319	POWER DIVIDERS & RF COMBINERS
Rotary Joints	322	ROTARY JOINTS
In-Line Surge Protectors; Replacement Cartridges	322	SURGE PROTECTORS
Electromechanical Relay Switches; SMT Packaged Electromechanical Relay Switches; Manual Switches; High Isolation USB Switches; High Isolation Switches; PIN Diode Switches GaN High Power Switches	324	SWITCHES
Synthesizers; Commercial Surface Mount Packaged VCO; Hermatically Sealed MIL Grade Surface Mount Packaged VCO; Connectorized Packaged VCO, Reference Oscillators, TCXO Oscillators, Phase Locked Oscillators and Phase Locked Crystal Oscillators	336	SYNTHESIZERS & OSCILLATORS
Equal Split; Unequal Split	341	TAPPERS
RF Load Terminations; Feed-Thru Load Terminations; Resistive Impedance Transformers	342	TERMINATIONS & MATCHING PADS
1.0mm Flexible VNA Test Cables; 26.5, 40, 50, 67 GHz and 75 Ohm Test Cables; Calibration Kits; Handheld RF Analyzer Rugged Stable Cable Assemblies; PE-TC151 and PE-TC195 Series Phase Stable Test Cable Assemblies; Semi-Rigid Pigtail Test Probes; VNA Test Cable Assemblies, etc.	348	TEST & MEASUREMENT PRODUCTS
Cable Cutters; Crimp Tools; Crimp Tool Dies ; Insertion/Extraction Tools; Torque Wrenches	355	TOOLS
WG Antennas; WG Bandpass Filters; WG Bends; WG Bulkhead Adapters; WG Converters; WG Couplers; WG Detectors; WG Direct Read Atten.; WG EMS; Flexible WG; WG Gunn Oscillators; WG Magic Tees; WG Phase Shifters; WG PIN Diode Switches; WG Power Amps., etc.	358	WAVEGUIDES
Pasternack REACH and RoHS Compliance Programs; Mailing List Changes; Binding Terms/Warranty; Part Number Index; Mounting Holes; Connector Identifiers; Connector Frequency Range Chart; Conversion Tables	390	APPENDIX

The information contained in this catalog and on pasternack.com is accurate to the best of our knowledge at the time of publication. It may be necessary to make modifications to the parts and/or the documentation of the parts, in order to implement improvements. Pasternack reserves

TABLE OF CONTENTS

5G Solutions
The 5G Outlook ... 5
RF Interconnects ... 6
RF Actives ... 6
RF Passives ... 7
Antennas ... 8

Adapters
Adapters to All Connectors ... 18
Locator (Part Number Identifier) ... 10
Low PIM Adapters ... 16
Quick Reference Guide ... 9
Selection Guide ... 9

Amplifiers
Locator ... 49
Quick Reference Guide ... 49
Selection Guide ... 49
Bi Directional Amplifiers ... 51
Broadband Amplifiers ... 51
DC Coupled Amplifiers ... 53
Gain Block Amplifiers ... 53
GaN High Power Amplifiers ... 58
Input Protected Low Noise Amplifiers ... 55
Limiting Amplifiers ... 53
Log Amplifiers ... 54
Low Noise Amplifiers ... 54
Power Amplifiers ... 55
Variable Gain Amplifiers ... 59

Antennas
Antenna Mounts ... 67
Directional Antennas ... 60
Omni Directional Antennas ... 62

Attenuators, Active
Locator ... 68
Quick Reference Guide ... 68
Selection Guide ... 68
Programmable Attenuators ... 85
Voltage Variable Attenuators ... 85

Attenuators, Passive
Locator ... 68
Quick Reference Guide ... 68
Selection Guide ... 68
Continuously Variable Attenuators ... 85
DC Bias Attenuators ... 84
Fixed Attenuators ... 70
Step Attenuators, Push Button ... 83
Step Attenuators, Rotary ... 84
Step Attenuators, Toggle ... 83

Baluns
Surface Mount ... 86

Bias Tee
Bias Tee ... 87

Cable Assemblies
Locator (By connector Type) ... 89
Low PIM and High-Reliability Cable Assemblies ... 93
Precision and Standard Cable Assemblies ... 96
Quick Reference Guide ... 88
Selection Guide ... 88

Circulators
2.92mm Connectors ... 222
N Connectors ... 222
SMA Connectors ... 222

Coaxial Cables
75 Ohm Broadcast ... 226
Communications ... 226
High Performance ... 227
RG Mil-C-17 Type Cable ... 227
Semirigid and Formable ... 228
Twinax Cable ... 230

Connectors
Locator (Part Number Identifier) ... 231
Quick Reference Guide ... 231
Selection Guide ... 231

Connector Caps
Non-Shorting Caps ... 300
Shorting Caps ... 301

Couplers
90 degree Hybrid ... 306
180 degree Hybrid ... 307
Directional ... 302
Dual Directional ... 305

DC Blocks
1.85mm ... 87
2.4mm ... 87
2.92mm ... 87
BNC ... 87
N ... 87
SMA ... 87
TNC ... 87
BNC ... 87
F ... 87
N ... 87

Detectors
Biased Detectors ... 315
Finline Detectors ... 315
Log Detectors ... 315
Phase Detectors ... 315
Power Detectors ... 316
Schottky Zero Bias Detectors ... 316
Threshold Detectors ... 316
Tunnel Diode Zero Bias Detectors ... 316

RF Diplexers
Low Pass and High Pass ... 307

Equalizers
Positive Slope Equalizers ... 86

Filters
Band Pass ... 310
Band Reject ... 310
Chebyshev Filters ... 309
Combline Filters ... 308
High Pass Filters ... 309
Low Pass Filters ... 309

Frequency Dividers
SMA Connectors ... 310

Frequency Multipliers
Active ... 313
Passive Doublers ... 313

Isolators
2.4mm Connectors ... 223
2.92mm Connectors ... 223
N Connectors ... 223
SMA Connectors ... 223

Limiters
HIGH REL ... 314
PIN-PIN ... 314
PIN-Schottky ... 314

Manual Switches
Manual Switches ... 331

Matching Pads
Resistive Impedance Transformers ... 347

Mixers
Double Balanced ... 311
IQ ... 311
Triple Balanced ... 312

Modulators
BiPhase ... 312

Noise Sources
Precision ... 317
SMT Pin Packaged ... 317
Standard ... 317

Oscillators
0.175" Ultra Small Commercial Surface Mount Packaged VCO ... 337
0.5" Commercial Surface Mount Packaged VCO ... 337
0.5" Commercial Surface Mount Packaged VCO w/ Integrated Buffer Amps ... 338
0.5" Commercial Surface Mount Packaged VCO w/ Low Noise ... 338
0.5" Commercial Surface Mount Packaged VCO w/ Modulation Input Port ... 339
0.5" Hermatically Sealed MIL Grade Surface Mount Packaged VCO ... 339
Connectorized Packaged VCO w/ Field Replaceable Connectors ... 339
Phase Locked Crystal Oscillators ... 341
Phase Locked Oscillators ... 341
Reference Oscillators ... 340
TCXO Reference Oscillators ... 340

Phase Shifters
8 Bit Programmable Phase Shifter ... 318
Adjustable Phase Shifter ... 318
Analog Phase Shifter ... 319

Phase Trimmers
Adjustable Phase Trimmer ... 318

Power Dividers
... 319
Reactive ... 319
Resistive ... 320
Wilkinson ... 320

RF Combiners
Broadband ... 322

Rotary Joints
SMA ... 322
2.92mm ... 322
SMA ... 322

Surge Protectors
In-Line Surge Protectors ... 322
Surge Protector Replacement Cartridges ... 323

Switches
Electromechanical Relay Switches ... 324
Electromechanical Relay Switches, SMT Packaged ... 330
GaN High Power Switches ... 335
High Isolation PIN Diode Switches ... 335
High Isolation USB PIN Diode Switches ... 335
PIN Diode Switches ... 331

Synthesizers
Integer/Fractional ... 336

Tappers
Equal Split ... 341
Unequal Split ... 342

Terminations
Feed-Thru Load ... 347
RF Load ... 343

Test And Measurement
1.0mm Flexible VNA 110 GHz Precision Cables ... 352
26.5 GHz and 40 GHz Test Cables ... 354
40 GHz Skew Matched Cable Pairs ... 350
4-in-1 Calibration Kits ... 349
50 GHz and 67 GHz Test Cable Assemblies ... 351
75 Ohm Test Cable Assemblies ... 354
Bench Type Calibration Kits ... 348
Handheld RF Analyzer Rugged Phase Stable Cable Assemblies ... 350
Interchangeable Connectors ... 349
PE-TC151 Series Phase Stable Test Cable ... 353
PE-TC195 Series Phase Stable Test Cable ... 353
RF Microwave Probes ... 349
Semi-Rigid Pigtail Test Probes ... 354
VNA Ruggedized Test Cable ... 351

Tools
Cable Cutter ... 355
Crimp Tool Dies ... 357
Crimp Tools ... 357
Insertion/Extraction Tool ... 355
Torque Wrenches ... 356

Waveguides
Flexible Waveguides ... 380
Waveguide Accessories ... 388
Waveguide Antennas ... 360
Waveguide Antennas Accessories ... 365
Waveguide BandPass Filters ... 369
Waveguide Bends ... 369
Waveguide Bulkhead Adapters ... 370
Waveguide Converter Mixers ... 371
Waveguide Couplers ... 371
Waveguide Detectors ... 377
Waveguide Direct Read Attenuators ... 377
Waveguide Double Ridge Bends ... 370
Waveguide Double Ridge Sections ... 385
Waveguide Electromechanical Relay Switches ... 377
Waveguide Fixed Attenuators ... 379
Waveguide Gunn Oscillators ... 381
Waveguide Isolators ... 381
Waveguide Low Noise Amplifiers ... 382
Waveguide Magic Tees ... 382
Waveguide Orthomode Transducers ... 382
Waveguide Phase Shifters ... 382
Waveguide PIN Diode Switches ... 383
Waveguide Polarizers ... 383
Waveguide Power Amplifiers ... 383
Waveguide Sections ... 383
Waveguide Terminations ... 385
Waveguide Transitions ... 386
Waveguide Twists ... 387
Waveguide Variable Attenuators ... 388

HELPFUL RESOURCES

Connector Freq. Range Chart ... 414	Mounting Hole Layout ... 409
Connector Identifier ... 410	Part Number Index ... 395
Conversion Tables ... 407	REACH-RoHS Compliance Program ... 391
How to Place your Order ... 392	Terms & Conditions ... 392

NEW PRODUCT ADDITIONS

RF Loads with Frequencies up to 67 GHz (See pages 343)

- Operating frequency range up to 67GHz
- Coaxial designs with 1.85mm, 2.4mm, 3.5mm, SMP and
- Mini-SMP connectors
- Available in both male/female connectorized configurations
- Flat RF response and performance
- Excellent VSWR performance as low as 1.15:1

ProLine Series Standard Gain Waveguide Horn Antennas (See pages 360-368)



- Complete line of high-performance waveguide antennas
- US made and TAA compliant
- Operating from 1.7 GHz to 40 GHz
- L, S, C, X, Ku, K, and Ka Band Operation
- Gain options of 10, 15 and 20 dBi
- WR-28 to WR-430 sizes available
- Type N, SMA, and 2.92mm (Type K) connectors available
- Ideal for applications such as: Antenna Measurements, Laboratory Use, Wireless Communications, Microwave Radio Systems

High-Power RF and Microwave PIN Diode Coaxial Packaged Switches (See pages 332, 335)



- GaN Semiconductor PIN Diode Switch Technology
- 50 Ohm Reflective Designs Cover Broadband Frequencies ranging from DC to 18 GHz
- High RF input power handling up to 100 watts CW
- Switching Speed 50 to 100 nsec typical
- Insertion Loss: 0.9 to 1.5 dB typical
- Compact and Rugged Mil Grade Coaxial Packaged Designs with Integrated TTL Compatible Drivers
- Models available with and without heatsinks

Input Protected Low Noise Amplifiers (See pages 55)

- GaN Semiconductor Technology
- Broadband Frequencies ranging from 1 - 23 GHz
- High RF input power handling up to 10 watts CW
- High gain up to 44 dB typ
- Low Noise Figure as low as 1.5 dB typ
- Rugged Mil-Grade SMA Connectorized Packaging

Coaxial Packaged Voltage Controlled Oscillators (VCO) Cover Broad Frequency Bands (See pages 340)

- Frequency bands ranging from 230 MHz to 5420 MHz
- Output power ranging from 0 dBm to +9 dBm
- Exceptional phase noise performance as low as -110 dBc/Hz at 10 KHz offset
- Internal voltage regulation and reverse DC protection.

Sub-6 GHz RF Antennas for 5G (See pages 62, 65, 66)

- Antennas designed for operation in sub-6 GHz 5G frequency bands
- Great for public or private 5G networks
- Options are available to cover from 600 MHz up to 7.2 GHz
- Connectors available in Type N or SMA
- In stock and ready to ship same day

Waveguide Components Include WRD-180, WRD-650 and WRD-750 Sizes (See pages 368, 370, 385-387)

- Wider operating frequency ranges than regular waveguide components (from 6.5GHz to 40GHz)
- Waveguide sizes: WRD-180, WRD-650 and WRD-750
- UG-style square cover flanges
- Manufactured with precision machining to ensure excellent RF performances

Micro-Sized EM Switches offer DC to 26 GHz Performance (See pages 330)

- 6 models cover broadband frequencies ranging from DC to 26 GHz
- SPDT Designs feature Latching Actuators with long and reliable lifespans up to 5M lifecycles typical
- Impressive Performance with very low insertion loss, high Isolation, and excellent repeatability
- True SMT Package concept has high thermal resistance and can use a variety of solder mounting processes
- Hot Switching capability up to 40W Average Power
- Models are RoHS and REACH Compliant

Rubber Duck Antennas offer Gain of 2 to 7 dBi and Frequencies of 900 MHz and 2.4 GHz (See pages 66)

- Antennas suitable for multiple applications in the 900 MHz and 2.4 GHz ISM space
- Functional in US, EU and Global RFID needs
- RIGID connections and Tilt and Swivel knuckle options available
- Gain from 2 dBi up to 7 dBi
- N Type, SMA, Reverse Polarity SMA and Reverse Polarity TNC connector options
- Economically priced for the entry level designer and upgrade opportunities
- Functional for IoT and automation applications
- In-stock and ready to ship same-day

NEW PRODUCT ADDITIONS

Yagi Antennas Operate at 400 / 900 MHz and Can Withstand Sustained Winds up to 200 mph (See pages 61)

- Yagi antennas offering 400 to 470 MHz (400 MHz band) and 880 to 960 MHz (900 MHz band) configurations
  Aircraft-quality aluminum with 1" boom and 5/16" elements
- Black powder-coated for corrosion, fade, and ice build-up resistance
- 200 mph wind survivability
- Gain options of 7 dBi to 13 dBi
- Antennas come fully welded for maximum durability
- In-stock and available for same-day shipping

Amplifier Models Cover Popular VHF/UHF, L, S and C Frequency Bands (See pages 51)

- 6 bi-directional amplifier models cover popular VHF/UHF, L, S, and C frequency bands
- Several designs incorporate highly efficient GaN semiconductor technology
- Transmit (Tx) output Psat levels range from 8 to 20 watts that boost performance of data links and transmitters
- Designs offer sensitive receiver performance with 2.5 dB noise figure
- Models feature manual or auto-sensing transmit/receive (T/R) control with fast switching times of 1-2 ºsec
- Rugged mil-grade designs are in compact, environmentally-sealed SMA connectorized packages

PCB Antennas Support Frequencies Ranging from 700 MHz to 5 GHz (See pages 65, 63)

- Variety of low profile/compact shapes and sizes to meet your design requirements
- Support for multiband cellular, NB-IoT, LTE-M, WiFi, WLAN and GPS
- Miniaturized connectors compatible with UMCX, IPEX and U.FL
- Highly efficient PCB designs for maximum embedded performance

Antennas Address ISM, RFID, SCADA, IoT and Utility Network Applications (See pages 60-67)

- Antennas suitable for multiple applications in the 900 MHz ISM space
  Functional in US, EU and global RFID needs
- Variety of polarization options to best fit the environment
- Point to multipoint & Non Line of Sight (NLOS) applications
  RFID & SCADA
- LPWAN, LoRA, IoT, M2M
- In stock and ready to ship same day

Waveguide-to-Coax Adapters with European IEC Standard Flanges (See pages 365-368)

- Frequency ranges from 1.72GHz to 40 GHz in 15 waveguide bands
- Waveguide sizes from WR-28 to WR-430
- European IEC standard flanges: UDR, PDR and UBR
- Coaxial designs: SMA, 2.92mm, N-Type and 2.4mm connectors
- Constructed with precision machining in brass or aluminum
- Available in right-angle and end-launch configurations

VNA Test Cables Boast Flex Life Exceeding 100,000 Cycles (See pages 100, 214, 351-352)

- Max phase variation +/- 6° to 50 GHz and +/- 8° to 70 GHz with flexure
  VSWR of 1.3:1 to 50 GHz and 1.4:1 to 70 GHz
  Standard and NMD 1.85mm and 2.4mm connector options
- Flexible VNA cable series rated up to 5,000 mating cycles
- Up to 100,000 flex cycles
- Swept right angle connector options available
- Highly flexible stainless steel braided armoring
- Designed for accurate and repeatable measurements

Field Replaceable Connectors Include SMA, 3.5mm, 2.92mm, 2.4mm, and 1.85mm Options (See pages 238, 240-241, 273-274)

- 4 Connector series SMA, 2.92mm, 2.4mm, and 1.85mm
- 2-Hole and 4-hole flange types
- Contacts mate with 5 pin diameters ranging from 0.009" to 0.036"
- Metal ground contact rings
- Allows for replacement of damaged connectors without accessing sealed components
- Multiple connector series can be used with a single mating pin diameter

Circulators/Isolators Cover Operating Frequency Ranges up to 42.5 GHz (See pages 222-224)

- Operating frequency ranges up to 42.5GHz
- Max. power rating up to 100W
- Available in SMA, N-type, 2.4mm and 2.92mm connectorized designs
- Broad spectrum of product selection available

SMT Noise Sources Cover Freq. from 0.2 MHz-3 GHz and are Ideal for PWB Applications (See pages 317)

- SMT gullwing pin and dual inline pin (DIP) surface mount packaging options with Frequency Bands range from 0.2-3 GHz
- Models generate additive white Gaussian noise (AWGN) output
- SMT gullwing pin models have high output ENR levels up to 51 dB
- Dual inline pin (DIP) models generate a noise output power level of -5 dBm
- Rugged 50 Ohm designs have operating temperature ranges up to -55°C to +125°C

The 5G Outlook

5G promises to deliver lightning-speed data rates, increased user capacity, reduced latency, and overall improved network efficiencies through new delivery technologies and distribution techniques like network splicing. Although many factors affect network speed, 5G will be at least 10 times faster than 4G networks, which often average less than 10 Mbps.
The global 5G infrastructure being built today will be the backbone of RF wireless innovation for years to come and also enable a new era for big data, where near-real-time processing and intelligence shared to and from a pleothera of connected devices will provide enhanced user experiences, safety, and responsiveness.

New 5G devices and applications are in various stages of development, testing and deployment. Three major use cases for 5G have been defined:

Mission Critical Applications

Including autonomous vehicles, remote health care, intelligent grids, industrial automation, and more – where low latency, ultra-high reliability connectivity is essential.

Enhanced Mobile Broadband

Offering increased speed and capacity through further rollout of MIMO, small cell, DAS, and fixed wireless technologies.

The Internet of Things (IoT)

Comprised of billions of connected devices, communicating without human intervention, creating new opportunities for big data exchange and analysis, and set to revolutionize manufacturing, business communications, agriculture, and more.

5G Solutions from Pasternack

RF Components for the Next Generation.....see web

Pasternack meets the urgent needs of engineers and technicians around the world for high-grade RF components and cable assemblies to support 5G innovation development, testing and deployments in the global sub-6 GHz (e.g. the 3.5 GHz mid-band) and mmWave bands (e.g. 26 GHz, 28 GHz and 39 GHz).

All Pasternack 5G solutions components are in-stock and shipped same day, and they are backed by first-class technical and engineering support. Our applications engineers are standing by ready to assist with answering your questions and selecting the right product for your specific application. Visit us online at Pasternack.com to view detailed datasheets, CAD drawings, real-time pricing and inventory, or to place your order and have it shipped today!

RF Interconnects

Connectors.....see web

Configure and customize your signal exactly as required with Pasternack's ready-to-ship RF connectors for 5G applications.

- A variety of options for size, frequency, signal power, PIM, durability, and space limitations
- Optimized for premium VSWR and PIM levels

Adapters.....see web

Get the reliable performance you expect and protect expensive test equipment with Pasternack's ready-to-ship RF adapters for 5G applications.

- A variety of options for size, frequency, signal power, PIM, durability, and space limitations
- Optimized for premium VSWR and PIM levels

Cable Assemblies.....see web

Count on the high-performance and rugged reliability of Pasternack's ready-to-ship RF cable assemblies for your 5G application.

- Low PIM in a variety of diameters and connector options
- Low VSWR and insertion loss
- Excellent phase stability under flexure
- Maximum operating frequencies up to 110 GHz, depending on cable type

RF Actives

Amplifiers.....see web

Expect reliable signal amplification with Pasternack's ready-to-ship, connectorized RF amplifiers for 5G applications.

- Over 65 models ideal for sub-6 GHz and mmWave frequency bands
- Amplifier designs include: bench-top, broadband, gain block, GaN power, high power, input protected low noise, limiting, low noise, waveguide, power, rack mount, USB, variable gain

Phase Shifters / Trimmers.....see web

Reliably convert frequencies with Pasternack's ready-to-ship, high-quality RF phase shifters and trimmers for 5G applications

- Covering select frequency bands up to 40 GHz and adjustable up to 120 degrees
- Available in manual-programmable varieties



5G Use Cases in a Shared

Switches.....see web

Meet your signal processing requirements with Pasternack's ready-to-ship RF electromechanical relay and PIN diode switches for 5G applications.

- Covering broadband frequencies DC to 40 GHz
- Over 165 models available in coaxial, waveguide, and SMT packaged configurations

Mixers and Multipliers.....see web

Expect high-performance signal conversion with Pasternack's ready-to-ship RF mixers and multipliers for 5G applications.

- Coaxial packaged mixers and multipliers covering select frequency bands from DC to 46 GHz
- Available in double-balanced, triple-balanced and IQ designs, with LO drive levels ranging from 10 to 19 dBm

Programmable Attenuators.....see web

Ensure reliable attenuation levels with Pasternack's ready-to-ship RF programmable attenuators for 5G applications.

- Covering sub-6 GHz and mmWave frequency bands
- Maximum attenuation levels up to 127 dB
- Designs optimized for low insertion loss and excellent VSWR as low as 1.25:1

Limiters and Detectors.....see web

Keep control of I/O power levels with Pasternack's ready-to-ship, broadband coaxial packaged RF limiters and detectors for 5G applications.

- Over 15 limiters and 20 detectors available for sub-6 GHz or mmWave frequency bands
- Available in compact cylindrical or drop-mountable package outlines with SMA or 2.92 mm RF connectors
- Ideal for proof-of-concept and prototyping in precision test and measurement, instrumentation, and subsystem assemblies



l Network Infrastructure

Noise Sources.....see web

Meet your immediate requirements for signal performance testing with Pasternack's ready-to-ship RF coaxial packaged noise sources for 5G applications.

- Over 25 models covering sub-6 GHz and mmWave frequency bands
- Noise source design configurations include: octave band and broadband, amplified, precision-calibrated instrumentation-grade, noise sources with integral isolators
- Most models designed to meet MIL-STD-202F environmental test conditions

Oscillators.....see web

Count on high-performance signal generation with Pasternack's ready-to-ship RF oscillators for 5G applications.

- Covering select bands from 10 MHz to 43 GHz
- Oscillator types include: voltage controlled (VCO), reference, phase locked, phase locked crystal, temperature compensated crystal
- Surface mount and coaxial packaged versions available

RF Passives

Power Dividers.....see web

Meet your immediate needs for 2-way and 4-way input power division with Pasternack's ready-to-ship RF power dividers for
5G applications.

- Maximum input power of 30 W for wideband operating frequency ranges up to 6 GHz
- Maximum input power of 20 W for operating frequency ranges in the mmWave bands

Fixed Attenuators.....see web

Provide reliable signal attenuation with Pasternack's line of ready-to-ship RF fixed attenuators for 5G applications.

- Wide range of attenuation levels and rated up to 2 W
- Maximum operating frequencies up to 6 GHz and mmWave bands
- Durable stainless steel construction
- Available in SMA and 2.92 mm connector designs

Terminations.....see web

Expect durable, high-performance with Pasternack's ready-to-ship RF terminations for 5G applications.

- Rated up to 2 W with maximum operating frequencies up to 6 GHz, 18 GHz, or 40 GHz
- Reliable stainless steel construction
- Available in SMA, Mini SMP, Type-N, 4.3-10, and 2.92 mm connector series

Filters.....see web

Turn to Pasternack for your RF bandpass filter needs for 5G applications.

- Covering mid-band and mmWave band frequencies
- 4, 9, and 11 section options
- SMA connector package design
- Low insertion loss and excellent VSWR

Directional Couplers.....see web

Expect high-quality signal coupling performance with Pasternack's ready-to-ship RF directional couplers for 5G applications.

- Wide range of coupling levels available and maximum input power levels as high as 30 W
- Operating frequency ranges up to the mmWave bands and operating temperature range from -45 to 85 degree C
- SMA and 2.92 connector designs available

Waveguides.....see web

Enable low loss transmission with Pasternack's ready-to-ship, precision waveguide components for 5G applications.

- mmWave operating frequency bands and Wide range of waveguide sizes
- Waveguide components include: couplers, waveguide-to-coax adapters, straights, bends, twists, and more

DC Blocks.....see web

Protect your bias-sensitive RF components with Pasternack's ready-to-ship, high-grade RF DC blocks for 5G applications.

- Maximum operating frequency ranges up to the mmWave band
- Inner or outer conductor configuration options available
- 2.92 mm, SMA, Type-N, and TNC connector designs available

Bias Tees.....see web

Ensure dependable signal processing with Pasternack's ready-to-ship RF bias tees for 5G applications.

- Maximum operating frequencies in the sub-6 GHz or mmWave frequency bands
- Maximum DC voltage rating of 100 V and current rating of 2.5 A
- SMA, Type-N, 3.5 mm, and 2.92 mm connector options available

5G Efficiencies

10x
Decrease in Latency
Delivering latency as low as 1 ms

3x
Spectrum Efficiency
Achieving even more bits per Hz with advanced antenna techniques

10x
Experience Throughput
Bringing more uniform, multi-Gbps peak rates

10x
Connection Density
Enabling more efficient signaling for IoT connectivity

100x
Traffic Capacity
Driving network hyper-densification with more small cells everywhere

100x
Network Efficiency
Optimizing network energy comsumption with more efficient processing

Antennas

RF and Waveguide Antennas.....see web

Explore Pasternack's wide selection of ready-to-ship RF and waveguide antennas for 5G applications.

- Operating in the sub-6 GHz and mmWave frequency bands
- Including coax fed antennas operating at sub-6 GHz
- Comprehensive offering of waveguide antennas including: standard gain horns, conical horns, scalar feed horns, lens horns, omni-directional with waveguide flanges
- Waveguide antennas mount directly to waveguides or can be combined with waveguide-to-coax adapters for coaxial connections

Adapter Selection Guide

3 Easy Ways to Find your Product.....

1. Search by PE Part Number

If you know the PE part number you are searching for, please reference our Part Number Index on Page 395

2. Quick Reference Guide

(Page number refers to first appearance of product in the Adapter Section)

Connector Series	Page
1.0/2.3	36
1.0mm	18
1.85mm	18
10-32	25
2.4mm	18
2.4mm NMD	19
2.92mm	18
2.92mm NMD	21
3.5mm	18
3.5mm NMD	22
4.1/9.5 Mini DIN	22
4.3-10	22

Connector Series	Page
7/16 DIN	23
75Ω BNC	45
75Ω F	26
75Ω Mini SMB	46
75Ω N	46
75Ω PAL	45
75Ω RCA	26
75Ω SMB	26
75Ω SMC	26
75Ω TNC	46
78Ω BNC Twinax	48
7mm	19

Connector Series	Page
95Ω 3/4"-20 Twinax	48
Banana	48
BMA	25
BNC	22
BNC Triax	26
C	26
Double Banana	26
D-Sub	26
FME	26
GR874	27
HN	24
LC	27

Connector Series	Page
MCX	28
MHV	26
Mini SMP	19
Mini UHF	28
MMBX	29
MMCX	29
N	18
QMA	31
Rev Pol MCX	40
Rev Pol N	30
Rev Pol SMA	35
Rev Pol TNC	33

Connector Series	Page
SC	24
SHV	28
SMA	19
SMB	31
SMC	31
SMP	19
SSMA	21
SSMB	37
SSMC	40
TNC	31
UHF	32
UMCX	38

Adapter Locator Layout

Connector Type	Feature	Model No.	C/R	Page
Indicates Connector Series Example: SMA, BNC,TNC, N	Contains a 1 or 2 Letter Code Example: (B) - Bulkhead (PO) - Push On	Adapter Part Number	Location of part on grid using Columns & Rows	Product Page Number

3. Between-Series Adapter Locator

(Adapter Locator starts on Page 10)



SMA FEMALE TO TNC FEMALE
PE9079

SMA Female To: EXAMPLE

Connector Type	Feature	Model No.	C/R	Page
SSMA Male		PE9188	A4	163
SSMB Plug		PE9402	A3	167
TNC Female		**PE9079**	D6	164
TNC Female	(B)	PE9251	A1	165

TNC Female To: EXAMPLE

Connector Type	Feature	Model No.	C/R	Page
SMA Female	(P)	PE9442	C6	164
SMA Female		**PE9079**	D6	164
SMA Female	(B)	PE9251	A1	165
SMA Female	(PM)	PE9276	B1	165

The Adapter Locator example above includes Between-Series part numbers in two configurations:
Connector 1 to Connector 2 as well as Connector 2 to Connector 1 can be found in the same location.

Products can only be found under the first instance of the series combination. As an example, PE9079 above will be found in only one location in the Adapter Section.

Adapter Locator

Connector Type	Feature	Model No.	C/R	Page
1.0/2.3 Jack To:				
SMA Female		PE9693	C1	38
SMA Male		PE9690	D2	36
1.0/2.3 Plug To:				
SMA Female		PE9691	B1	38
SMA Male		PE9692	C2	36
1.0mm Female To:				
1.85mm Female		PE91109	D2	18
1.85mm Male		PE91119	C2	18
1.0mm In-Series:				
Female to Female		PE91463	D1	18
Female to Male		PE91461	C1	18
Male to Male		PE91462	B1	18
1.0mm Male To:				
1.85mm Female		PE91108	B2	18
1.85mm Male		PE91118	A2	18
1.85mm Female To:				
1.0mm Female		PE91109	D2	18
1.0mm Male		PE91108	B2	18
2.4mm Female	90º	PE91534	A6	18
2.4mm Female		PE9675	D4	19
2.4mm Male		PE9674	E2	19
2.92mm Female	90º	PE91163	D6	18
2.92mm Female	90º	PE91513	E6	18
2.92mm Male	90º	PE91162	B6	18
2.92mm Male	90º	PE91512	C6	18
2.92mm Male		PE9666	A3	20
3.5mm Female		PE9748	A7	21
3.5mm Male		PE9745	B5	21
N Female		PE9721	B7	18
N Male		PE9720	A7	18
SMA Female		PE9729	E1	38
SMA Male		PE9728	A3	36
1.85mm In-Series:				
Female to Female		PE91084	E3	18
Female to Female		PE91115	A4	18
Male to Female		PE91086	C3	18
Male to Female		PE9715	D3	18
Male to Male		PE91085	A3	18
Male to Male		PE9716	B3	18
1.85mm Male To:				
1.0mm Female		PE91119	C2	18
1.0mm Male		PE91118	A2	18
2.4mm Female	90º	PE91511	E4	18
2.4mm Female		PE9673	B4	19
2.4mm Female	(P)	PE91542	C4	19
2.4mm Male	90º	PE91157	C4	18
2.4mm Male	90º	PE91518	D4	18
2.4mm Male		PE9672	C2	19
2.4mm Male		PE91540	D2	19
2.92mm Female		PE9665	B6	20
2.92mm Male	90º	PE91161	A5	18
2.92mm Male	90º	PE91519	B5	18
2.92mm Male		PE9667	E2	20
3.5mm Female		PE9747	C5	18
3.5mm Male		PE9746	A5	21
N Female		PE9719	E5	18
N Male		PE9718	D5	18
SMA Female		PE9726	D1	38
SMA Male		PE9727	E2	36
10-32 Female To:				
BNC Female		PE9752	C2	25
BNC Female	(B)	PE9754	D2	25
BNC Male		PE9750	B2	25
10-32 In-Series:				
Female to Female		PE9756	A1	25
Female to Female	(B)	PE9757	B1	25
10-32 Male To:				
BNC Female		PE9753	E1	25
BNC Female	(B)	PE9755	A2	25
BNC Male		PE9751	D1	25
2.4mm Female To:				
1.85mm Female		PE9675	D4	19
1.85mm Female	90º	PE91534	A6	18
1.85mm Male		PE9673	B4	19
1.85mm Male	(P)	PE91542	C4	19
1.85mm Male	90º	PE91511	E4	18
2.4mm NMD Female		PE91145	E6	19
2.92mm Female	90º	PE91111	A5	19
2.92mm Female	90º	PE91525	B5	19
2.92mm Female		PE91499	E6	20
2.92mm Female		PE9456	A7	20
2.92mm Male	90º	PE91526	E4	19
2.92mm Male		PE91450	D3	20
2.92mm Male		PE9455	E3	20
2.92mm NMD Female		PE91144	E2	21
3.5mm Female		PE91291	C7	21
3.5mm Female		PE9652	D7	21
3.5mm Female		PE91547	E7	21
3.5mm Male		PE91452	E5	21
3.5mm Male		PE9651	A6	21
3.5mm NMD Female		PE91148	B2	22
Full Detent Mini SMP Male		PE91122	C5	19
Mini SMP Female		PE91123	D5	19
N Female	(P)	PE9502	A6	19
N Male	(P)	PE9503	E5	19
SMA Female	(P)	PE9656	B2	38
SMA Male	(P)	PE9654	C3	36

Connector Type	Feature	Model No.	C/R	Page
SMP Female		PE91055	C6	19
SMP Male		PE91048	B6	19
2.4mm In-Series:				
Female to Female		PE9453	C1	19
Female to Female	(B)	PE91459	D1	19
Female to Female	(B)	PE9640	E1	19
Female to Female	90º	PE91529	A2	19
Male to Female		PE9452	E7	18
Male to Female	90º	PE91138	A1	19
Male to Female	90º	PE91498	B1	19
Male to Male		PE9451	D7	18
2.4mm Male To:				
1.85mm Female		PE9674	E2	19
1.85mm Male		PE9672	C2	19
1.85mm Male		PE91540	D2	19
1.85mm Male	90º	PE91157	C4	18
1.85mm Male	90º	PE91518	D4	18
2.92mm Female	90º	PE91502	B3	19
2.92mm Female		PE91451	C6	20
2.92mm Female		PE9454	D6	20
2.92mm Male	90º	PE91508	A3	19
2.92mm Male		PE91298	B3	20
2.92mm Male		PE9457	C3	20
3.5mm Female		PE9650	B7	21
3.5mm Male		PE91294	C5	21
3.5mm Male		PE9649	D5	21
7mm Sexless		PE9458	C3	19
Full Detent Mini SMP Male		PE91121	D3	19
N Female	(P)	PE9501	A4	19
N Male	(P)	PE9504	E3	19
SMA Female		PE9655	A2	38
SMA Male	(P)	PE9653	B3	36
2.4mm NMD Female To:				
2.4mm Female		PE91145	E6	19
SMA Female	(RU)	PE91146	A7	19
2.92mm Female To:				
1.85mm Female	90º	PE91163	D6	18
1.85mm Female	90º	PE91513	E6	18
1.85mm Male		PE9665	B6	20
2.4mm Female		PE91499	E6	20
2.4mm Female		PE9456	A7	20
2.4mm Female	90º	PE91111	A5	19
2.4mm Female	90º	PE91525	B5	19
2.4mm Male		PE91451	C6	20
2.4mm Male		PE9454	D6	20
2.4mm Male	90º	PE91502	B3	19
2.92mm Male	(R)	PE91070	A4	20
3.5mm Female		PE9660	C7	20
3.5mm Female	90º	PE91167	D7	20
3.5mm Female	90º	PE91521	E7	20
3.5mm Male	90º	PE91520	B7	20
3.5mm Male		PE9658	B6	21
7mm Sexless	(P)	PE9461	A1	21
Full Detent Mini SMP Male		PE91127	B1	21
Mini SMP Female		PE9782	D1	21
N Female	(P)	PE9664	A2	21
N Male	(P)	PE9663	E1	21
SMA Female	(P)	PE91011	D2	38
SMA Male	(P)	PE91008	E3	36
Smooth Bore Mini SMP Male		PE91128	C1	21
SMP Female		PE91060	B2	21
SSMA Male		PE9768	C2	21
2.92mm In-Series:				
Female to Female		PE91510	B1	20
Female to Female		PE9438	C1	20
Female to Female	90º	PE91517	D1	20
Female to Female	(B) (PM)	PE9647	E1	20
Female to Female	(PM)	PE91113	A2	20
Female to Female	(PM)	PE9648	B2	20
Female to Female	(PM)	PE91538	C2	20
Male to Female		PE9437	E7	19
Male to Female	90º	PE91503	A1	20
Male to Male		PE9436	C7	19
Male to Male	90º	PE91516	D7	19
2.92mm Male To:				
1.85mm Female		PE9666	A3	20
1.85mm Female	90º	PE91162	B6	18
1.85mm Female	90º	PE91512	C6	18
1.85mm Male		PE9667	E2	20
1.85mm Male	90º	PE91161	A5	18
1.85mm Male	90º	PE91519	B5	18
2.4mm Female		PE91450	D3	20
2.4mm Female		PE9455	E3	20
2.4mm Female	90º	PE91526	E4	19
2.4mm Male		PE91298	B3	20
2.4mm Male		PE9457	C3	20
2.4mm Male	90º	PE91508	A3	19
2.92mm Female	(R)	PE91070	A4	20
3.5mm Female	90º	PE91168	D4	20
3.5mm Female	90º	PE91514	E4	20
3.5mm Female		PE9659	A1	22
3.5mm Male	90º	PE91165	B4	20
3.5mm Male	90º	PE91522	C4	20
7mm Sexless		PE9460	A5	20
Mini SMP Female		PE91126	D5	20
Mini SMP Male		PE91124	B5	20
N Female	(P)	PE9662	A6	20

Connector Type	Feature	Model No.	C/R	Page
N Male	(P)	PE9661	E5	20
SMA Female	(P)	PE91009	C2	38
SMA Male	(P)	PE91010	D3	36
Smooth Bore Mini SMP Male		PE91125	C5	20
2.92mm NMD Female To:				
2.4mm Female		PE91144	E2	21
3.5mm Female To:				
1.85mm Female		PE9748	A7	21
1.85mm Male		PE9747	C5	18
2.4mm Female		PE91291	C7	21
2.4mm Female		PE9652	D7	21
2.4mm Female		PE91547	E7	21
2.4mm Male		PE9650	B7	21
2.92mm Female		PE9660	C7	20
2.92mm Female	90º	PE91167	D7	20
2.92mm Female	90º	PE91521	E7	20
2.92mm Male		PE9659	A1	22
2.92mm Male	90º	PE91168	D4	20
2.92mm Male	90º	PE91514	E4	20
7mm Sexless	(P)	PE9325	B1	22
7mm Sexless	(P)	PE91546	C1	22
N Female	(P)	PE9323	E1	22
N Male	(P)	PE9321	D1	22
SMA Female		PE9725	A3	38
SMA Male		PE91536	B4	36
3.5mm In-Series:				
Female to Female	(B) (PM)	PE9678	B4	21
Female to Female	(PM)	PE9676	C4	21
Female to Female	90º	PE91528	D4	21
Male to Female		PE9332	E3	21
Male to Female	90º	PE91523	A4	21
Male to Male		PE9330	B3	21
Male to Male	90º	PE91169	C3	21
Male to Male	90º	PE91515	D3	21
3.5mm Male To:				
1.85mm Female		PE9745	B5	21
1.85mm Male		PE9746	A5	21
2.4mm Female		PE91452	E5	21
2.4mm Female		PE9651	A6	21
2.4mm Male		PE91294	C5	21
2.4mm Male		PE9649	D5	21
2.92mm Female		PE9658	B6	21
2.92mm Female	90º	PE91520	B7	20
2.92mm Male	90º	PE91165	B4	20
2.92mm Male	90º	PE91522	C4	20
7mm Sexless	(P)	PE9326	C6	21
N Female	(P)	PE9324	E6	21
N Male	(P)	PE9322	D6	21
SMA Female		PE9724	E2	38
SMA Male		PE9722	A4	36
3.5mm NMD Female To:				
2.4mm Female		PE91148	B2	22
SMA Female	(RU)	PE91147	C2	22
4.1/9.5 Mini DIN Female To:				
7/16 DIN Female		PE91208	D4	24
7/16 DIN Female		PE91245	E4	24
7/16 DIN Female	(LP)	PE91091	A5	24
7/16 DIN Female	(B)	PE91247	B5	24
7/16 DIN Male		PE91207	E1	24
7/16 DIN Male		PE91244	A2	24
N Female		PE91218	C6	22
N Female		PE91255	D6	22
N Female	(LP)	PE91095	E6	22
N Male		PE91219	E5	22
N Male		PE91256	A6	22
N Male	(LP)	PE91094	B6	22
4.1/9.5 Mini DIN In-Series:				
Female to Female		PE91233	A4	22
Female to Female	(B)	PE91197	B4	22
Female to Female	(B)	PE91234	C4	22
Male to Female		PE91195	E3	22
Male to Male		PE91194	C3	22
Male to Male		PE91231	D3	22
4.1/9.5 Mini DIN Male To:				
7/16 DIN Female		PE91209	A4	24
7/16 DIN Female		PE91246	B4	24
7/16 DIN Female	(LP)	PE91090	C4	24
7/16 DIN Male		PE91206	B1	24
7/16 DIN Male		PE91243	C1	24
7/16 DIN Male	(LP)	PE91088	D1	24
N Female		PE91217	B5	22
N Female		PE91254	C5	22
N Female	(LP)	PE91093	D5	22
N Male		PE91216	E4	22
N Male	(LP)	PE91092	A5	22
4.3-10 Female To:				
7/16 DIN Female	(LP)	PE91471	A6	24
7/16 DIN Male	(LP)	PE91469	C2	24
7/16 DIN Male	(LP)	PE91390	D2	24
N Female	(LP)	PE91475	E3	23
N Male	(LP)	PE91479	C3	23
N Male	(LP)	PE91388	D7	30
4.3-10 In-Series:				
Female to Female	(LP)	PE91464	B1	23
Female to Female	(LP)	PE91386	C1	23
Male to Female	(LP)	PE91465	D7	22
Male to Female	(LP) 90º	PE91467	E7	22

Feature: (B) Bulkhead Mount / (H) Hermetically Sealed / (I) Isolated Sealed / (LP) Low PIM / (P) Precision / (PM) Panel Mount / (PO) Push On / (QD) Quick Disconnect / (R) Radius Right Angle / (RU) Ruggedized / (SO) Snap-On

Adapter Locator

Connector Type	Feature	Model No.	C/R	Page
Male to Female	(LP)	PE91387	A1	23
Male to Male	(LP)	PE91466	B7	22
Male to Male	(LP)	PE91385	C7	22
4.3-10 Male To:				
7/16 DIN Female	(LP)	PE91470	C5	24
7/16 DIN Female	(LP)	PE91391	E5	24
7/16 DIN Male	(LP)	PE91468	B2	24
N Female	(LP)	PE91474	B2	23
N Female	(LP)	PE91477	C2	23
N Female	(LP) 90º	PE91483	E2	23
N Female	(LP)	PE91389	A3	23
N Male	(LP)	PE91476	E1	23
SMA Female	(LP)	PE91484	B3	23
7/16 DIN Female To:				
4.1/9.5 Mini DIN Female		PE91208	D4	24
4.1/9.5 Mini DIN Female		PE91245	E4	24
4.1/9.5 Mini DIN Female	(LP)	PE91091	A5	24
4.1/9.5 Mini DIN Female	(B)	PE91247	B5	24
4.1/9.5 Mini DIN Male		PE91209	A4	24
4.1/9.5 Mini DIN Male		PE91246	B4	24
4.1/9.5 Mini DIN Male	(LP)	PE91090	C4	24
4.3-10 Female	(LP)	PE91471	A6	24
4.3-10 Male	(LP)	PE91470	C5	24
4.3-10 Male	(LP)	PE91391	E5	24
HN Male		PE9559	C6	24
N Female		PE91213	A7	24
N Female		PE91250	B7	24
N Female	(B)	PE91215	C7	24
N Female	(B)	PE91252	D7	24
N Female	(LP)	PE91033	A2	32
N Female	(LP)	PE9180	B2	32
N Male		PE91214	D6	24
N Male		PE91251	E6	24
N Male	(LP)	PE91032	B1	31
N Male		PE91134	C1	31
QD 4.3-10 Female	(LP) (QD)	PE91473	B6	24
QD 4.3-10 Male	(LP) (QD)	PE91472	D5	24
SMA Female	(LP)	PE91042	A4	38
SMA Male		PE9411	D4	36
TNC Female		PE91392	D3	44
TNC Male		PE9638	D7	43
7/16 DIN In-Series:				
Female to Female		PE91192	B6	23
Female to Female		PE91229	C6	23
Female to Female	(LP)	PE91029	D6	23
Female to Female		PE9409	E6	23
Female to Female		PE9556	A7	23
Female to Female	(B) (LP)	PE91038	B7	23
Female to Female	(B)	PE9414	C7	23
Female to Female	(B)	PE91193	D7	23
Female to Female	(B)	PE91230	E7	23
Female to Male		PE9557	A6	23
Male to Female		PE91191	A5	23
Male to Female		PE91228	B5	23
Male to Female		PE91027	C5	23
Male to Female	(LP)	PE91028	D5	23
Male to Female	90º	PE91117	E5	23
Male to Male		PE91190	C4	23
Male to Male		PE91227	D4	23
Male to Male	(LP)	PE91039	E4	23
7/16 DIN Male To:				
4.1/9.5 Mini DIN Female		PE91207	E1	24
4.1/9.5 Mini DIN Female		PE91244	A2	24
4.1/9.5 Mini DIN Male		PE91206	B1	24
4.1/9.5 Mini DIN Male		PE91243	C1	24
4.1/9.5 Mini DIN Male	(LP)	PE91088	D1	24
4.3-10 Female	(LP)	PE91469	C2	24
4.3-10 Female	(LP)	PE91390	D2	24
4.3-10 Male	(LP)	PE91468	B2	24
HN Female		PE9558	E2	24
N Female		PE91212	C3	24
N Female		PE91249	D3	24
N Female	(LP)	PE91031	E1	32
N Male		PE91211	A3	24
N Male		PE91248	B3	24
N Male	(LP)	PE91030	E7	30
N Male		PE9535	A1	31
SC Female		PE91444	E3	24
SMA Female	(LP)	PE91036	D3	38
SMA Female		PE91175	E3	38
75 Ohm BNC Female To:				
75 Ohm F Female	(B)	PE91324	B4	45
75 Ohm F Female		PE9744	C7	45
75 Ohm F Male		PE9743	D6	45
75 Ohm Mini SMB Jack		PE9619	E2	46
75 Ohm Mini SMB Plug		PE9617	C2	46
75 Ohm N Female		PE9371	A7	46
75 Ohm N Male		PE9369	E4	46
75 Ohm TNC Male		PE9631	A7	47
75 Ohm BNC In-Series:				
Female to Female		PE9362	B3	45
Female to Female	(B)	PE9363	C3	45
Female to Female	(PM)	PE9367	D3	45
Female to Female	(B)	PE9791	E3	45
Female to Male		PE9365	A3	45
Male to Female	90º	PE9361	E2	45
Male to Male		PE9364	D2	45
75 Ohm BNC Male To:				
75 Ohm F Female		PE9741	B7	45
75 Ohm F Male		PE9742	C6	45
75 Ohm Mini SMB Jack		PE9618	D2	46
75 Ohm Mini SMB Plug		PE9616	B2	46
75 Ohm N Female		PE9368	E6	46
75 Ohm N Male		PE9370	D4	46
75 Ohm TNC Female		PE9630	D7	47
75 Ohm F Female To:				
75 Ohm BNC Female		PE9744	C7	45
75 Ohm BNC Female	(B)	PE91324	B4	45
75 Ohm BNC Male		PE9741	B7	45
75 Ohm N Female		PE9740	D7	46
75 Ohm N Male		PE9396	B5	46
75 Ohm PAL Jack		PE9634	D7	45
75 Ohm RCA Plug		PE9163	E7	45
75 Ohm TNC Female		PE91082	A1	48
75 Ohm TNC Male		PE91080	C7	47
BNC Female		PE9153	C4	26
BNC Male		PE9150	C2	26
N Male		PE9155	D3	31
SMA Female		PE91002	D5	38
SMA Male		PE91003	D5	36
UHF Female		PE9167	A2	45
UHF Male		PE9165	A1	45
75 Ohm F In-Series:				
Female to Female	(P)	PE91349	D5	45
Female to Female		PE9164	E5	45
Female to Female	(B) (PM)	PE9734	A6	45
Male to Female	(PO)	PE9160	A5	45
Male to Female		PE9759	B5	45
Male to Female	90º	PE9166	C5	45
Male to Male	(P)	PE91348	D4	45
Male to Male		PE9760	E4	45
75 Ohm F Male To:				
75 Ohm BNC Female		PE9743	D6	45
75 Ohm BNC Male		PE9742	C6	45
75 Ohm N Female		PE9397	B7	46
75 Ohm N Female		PE9739	C7	46
75 Ohm N Male		PE9738	A5	46
75 Ohm PAL Jack		PE9632	A7	45
75 Ohm PAL Plug		PE9633	E6	45
75 Ohm TNC Female		PE91083	E7	47
75 Ohm TNC Male		PE91081	B7	47
BNC Female		PE9151	B4	26
BNC Male		PE9152	B2	26
N Female		PE9389	D4	32
SMA Female		PE91045	C5	38
75 Ohm Mini SMB In-Series:				
Jack to Jack		PE9608	D1	46
Jack to Jack	(B)	PE9611	E1	46
Plug to Jack		PE9610	C1	46
Plug to Plug		PE9609	B1	46
75 Ohm Mini SMB Jack To:				
75 Ohm BNC Female		PE9619	E2	46
75 Ohm BNC Male		PE9618	D2	46
75 Ohm N Female		PE9615	A1	47
75 Ohm N Male		PE9614	D5	46
75 Ohm SMB Plug		PE9736	A4	47
75 Ohm Mini SMB Plug To:				
75 Ohm BNC Female		PE9617	C2	46
75 Ohm BNC Male		PE9616	B2	46
75 Ohm N Female		PE9613	E7	46
75 Ohm N Male		PE9612	C5	46
75 Ohm SMB Jack		PE9735	C4	47
75 Ohm N Female To:				
75 Ohm BNC Female		PE9371	A7	46
75 Ohm BNC Male		PE9368	E6	46
75 Ohm F Female		PE9740	D7	46
75 Ohm F Male		PE9397	B7	46
75 Ohm F Male		PE9739	C7	46
75 Ohm Mini SMB Jack		PE9615	A1	47
75 Ohm Mini SMB Plug		PE9613	E7	46
75 Ohm SMB Jack		PE9583	C1	47
75 Ohm SMB Plug		PE9585	B1	47
75 Ohm SMC Jack		PE9587	E1	47
75 Ohm SMC Plug		PE9589	D1	47
75 Ohm TNC Female		PE9629	B2	47
75 Ohm TNC Male		PE9628	A2	47
75 Ohm N In-Series:				
Female to Female		PE9306	E3	46
Female to Female	(B) (PM)	PE9417	A4	46
Female to Female	(B)	PE9416	B4	46
Male to Female		PE9391	C3	46
Male to Female	90º	PE9307	D3	46
Male to Male		PE9308	B3	46
75 Ohm N Male To:				
75 Ohm BNC Female		PE9369	E4	46
75 Ohm BNC Male		PE9370	D4	46
75 Ohm F Female		PE9396	B5	46
75 Ohm F Male		PE9738	A5	46
75 Ohm Mini SMB Jack		PE9614	D5	46
75 Ohm Mini SMB Plug		PE9612	C5	46
75 Ohm SMB Jack		PE9582	A6	46
75 Ohm SMB Plug		PE9584	E5	46
75 Ohm SMC Jack		PE9586	B6	46
75 Ohm TNC Female		PE9627	D6	46
75 Ohm TNC Male		PE9626	C6	46
75 Ohm PAL In-Series:				
Plug to Plug		PE9680	D2	47
75 Ohm PAL Jack To:				
75 Ohm F Female		PE9634	D7	45
75 Ohm F Male		PE9632	A7	45
75 Ohm PAL Plug To:				
75 Ohm F Male		PE9633	E6	45
75 Ohm Push-On RCA Jack To:				
BNC Male	(PO)	PE9171	E2	26
75 Ohm RCA Jack To:				
BNC Female		PE9015	E4	26
75 Ohm RCA Plug To:				
75 Ohm F Female		PE9163	E7	45
BNC Female		PE9158	D4	26
75 Ohm SMB In-Series:				
Jack to Jack		PE9248	C3	47
Jack to Plug		PE9245	B3	47
Plug to Plug		PE9271	A3	47
75 Ohm SMB Jack To:				
75 Ohm Mini SMB Plug		PE9735	C4	47
75 Ohm N Female		PE9583	C1	47
75 Ohm N Male		PE9582	A6	46
BNC Female		PE9231	A5	26
BNC Male		PE9229	B4	47
75 Ohm SMB Plug To:				
75 Ohm Mini SMB Jack		PE9736	A4	47
75 Ohm N Female		PE9585	B1	47
75 Ohm N Male		PE9584	E5	46
BNC Female		PE9232	E3	47
BNC Male		PE9230	A3	26
75 Ohm SMC In-Series:				
Jack to Jack		PE9227	A5	47
Jack to Jack	(B) (PM)	PE9228	B5	47
Jack to Plug		PE9244	E4	47
75 Ohm SMC Jack To:				
75 Ohm N Female		PE9587	E1	47
75 Ohm N Male		PE9586	B6	46
BNC Female		PE9235	D5	47
BNC Male		PE91044	C3	26
75 Ohm SMC Plug To:				
75 Ohm N Female		PE9589	D1	47
BNC Female		PE9236	B5	26
BNC Male		PE9234	B3	26
75 Ohm TNC Female To:				
75 Ohm BNC Male		PE9630	D7	47
75 Ohm F Female		PE91082	A1	48
75 Ohm F Male		PE91083	E7	47
75 Ohm N Female		PE9629	B2	47
75 Ohm N Male		PE9627	D6	46
75 Ohm TNC In-Series:				
Female to Female		PE9622	B6	47
Female to Female	(B) (PM)	PE9625	C6	47
Female to Female	(B)	PE9624	D6	47
Male to Female	90º	PE9623	A6	47
75 Ohm TNC Male To:				
75 Ohm BNC Female		PE9631	A7	47
75 Ohm F Female		PE91080	C7	47
75 Ohm F Male		PE91081	B7	47
75 Ohm N Female		PE9628	A2	47
75 Ohm N Male		PE9626	C6	46
78 Ohm BNC Twinax In-Series:				
Jack to Jack		PE9378	A2	48
Jack to Jack	(B)	PE9280	B2	48
Jack to Plug		PE9375	E1	48
Plug to Jack	90º	PE9377	D1	48
Plug to Plug		PE9376	C1	48
7mm Sexless To:				
2.4mm Male		PE9458	C3	19
2.92mm Female	(P)	PE9461	A1	21
2.92mm Male		PE9460	A5	20
3.5mm Female	(P)	PE9325	B1	22
3.5mm Female	(P)	PE91546	C1	22
3.5mm Male	(P)	PE9326	C6	21
BNC Female	(P)	PE9220	A3	22
BNC Male	(P)	PE9221	E2	22
N Female	(P)	PE9216	D1	32
N Male	(P)	PE9217	C7	30
SMA Female	(P)	PE9214	B3	38
SMA Female	(P) (PM)	PE9327	C3	38
SMA Male	(P)	PE9215	C4	36
TNC Female	(P)	PE9218	C3	44
TNC Male	(P)	PE9219	C7	43
95 Ohm 3/4"-20 Twinax In-Series:				
Female to Female		PE9199	E2	48
Female to Female	(B)	PE9373	A3	48
Female to Male		PE9374	D2	48
Banana Binding Post Jack To:				
BNC Male		PE9169	C4	48
Banana Plug To:				
BNC Female		PE9175	C3	48
BMA In-Series:				
Jack to Jack		PE91395	A3	25
BNC Female To:				
10-32 Female		PE9752	C2	25
10-32 Female	(B)	PE9754	D2	25
10-32 Male		PE9753	E1	25
10-32 Male	(B)	PE9755	A2	25
75 Ohm F Female		PE9153	C4	26

Feature: (B) Bulkhead Mount / (H) Hermetically Sealed / (I) Isolated Sealed / (LP) Low PIM / (P) Precision / (PM) Panel Mount / (PO) Push On / (QD) Quick Disconnect / (R) Radius Right Angle / (RU) Ruggedized / (SO) Snap-On

Adapter Locator

Connector Type	Feature	Model No.	C/R	Page
75 Ohm F Male		PE9151	B4	26
75 Ohm RCA Jack		PE9015	E4	26
75 Ohm RCA Plug		PE9158	D4	26
75 Ohm SMB Jack		PE9231	A5	26
75 Ohm SMB Plug		PE9232	E3	47
75 Ohm SMC Jack		PE9235	D5	47
75 Ohm SMC Plug		PE9236	B5	26
7mm Sexless	(P)	PE9220	A3	22
Banana Plug		PE9175	C3	48
C Female		PE9537	E3	26
C Female	(B) (PM)	PE9204	A4	26
C Male		PE9087	D3	26
Double Banana Binding Post Jack		PE9013	E4	48
Double Banana Plug		PE9008	A4	48
FME Jack		PE9712	E1	27
HN Male		PE9126	D5	27
MCX Jack		PE9466	B3	28
MCX Jack	(B) (PM)	PE9520	C3	28
MCX Plug		PE9467	E2	28
Mini UHF Male		PE9342	D7	28
MMCX Jack		PE9516	D3	29
N Female		PE9206	B3	32
N Female	(P)	PE9492	C3	32
N Female	(B) (PM)	PE9261	D3	32
N Female	(PM)	PE9238	E3	32
N Female	(B) (PM)	PE9540	A4	32
N Male		PE9002	B2	31
N Male	(P)	PE9491	C2	31
N Male	90º	PE9278	D2	31
N Male	(PM)	PE9388	E2	31
SC Female		PE9571	B7	33
SMA Female		PE9075	D4	38
SMA Female		PE9496	E4	38
SMA Female	(B)	PE9185	A5	38
SMA Female	(B)	PE9407	B5	38
SMA Male		PE9074	B5	36
SMA Male		PE9495	C5	36
SMB Jack		PE9136	D3	41
SMB Jack	(B)	PE9240	E3	41
SMB Plug		PE9137	A3	41
SMB Plug	(B) (PM)	PE9241	B3	41
SMC Jack		PE9140	E6	41
SMC Jack	(B)	PE9108	A7	41
SMC Plug		PE9141	A6	41
SSMA Male		PE91046	E4	42
SSMB Jack		PE9394	D6	42
SSMB Plug		PE9395	B6	42
TNC Female		PE9097	A4	44
TNC Male		PE9088	A1	44
TNC Male	90º	PE9783	B1	44
UHF Female		PE9421	E1	45
UHF Male		PE91328	E7	44
BNC In-Series:				
Female to Female		PE9084	C6	25
Female to Female		PE9003	D6	25
Female to Female	(B) (PM)	PE9420	E6	25
Female to Female	(B)	PE9093	A7	25
Female to Female	(B)	PE9172	B7	25
Female to Female	(PM)	PE9106	C7	25
Female to Male		PE9001	B6	25
Female to Male		PE9529	A1	26
Male to Female		PE9269	C5	25
Male to Female	90º	PE9085	D5	25
Male to Female		PE9174	E5	25
Male to Female		PE9484	A6	25
Male to Female		PE9530	E7	25
Male to Male		PE9000	A5	25
Male to Male	90º	PE9758	B5	25
BNC Male To:				
10-32 Female		PE9750	B2	25
10-32 Male		PE9751	D1	25
75 Ohm F Female		PE9150	C2	26
75 Ohm F Male		PE9152	B2	26
75 Ohm Push-On RCA Jack	(PO)	PE9171	E2	26
75 Ohm SMB Jack		PE9229	B4	47
75 Ohm SMB Plug		PE9230	A3	26
75 Ohm SMC Jack		PE91044	C3	26
75 Ohm SMC Plug		PE9234	B3	26
7mm Sexless	(P)	PE9221	E2	22
Banana Binding Post Jack		PE9169	C4	48
BNC Triax Female		PE91104	D1	26
C Female		PE9109	A2	26
C Male		PE9536	E1	26
Double Banana Binding Post Jack		PE9011	C1	26
Double Banana Plug		PE9009	E3	48
FME Jack		PE9711	D1	27
FME Plug		PE9697	B1	27
FME Plug	90º	PE9698	C1	27
GR874 Sexless		PE9223	E2	27
HN Female		PE9129	D6	27
HN Male		PE9567	C5	27
MCX Jack		PE9468	A3	28
MCX Plug		PE9469	D2	28
MHV Female		PE9406	D2	26
Mini UHF Female		PE9341	C1	29
MMCX Jack		PE9518	C3	29
MMCX Plug		PE9517	E2	29
N Female		PE9005	C2	32
N Female	(P)	PE9490	D2	32
N Female	90º	PE9566	E2	32
N Female	(PM)	PE9123	A3	32
N Male		PE9127	D1	31
N Male	(P)	PE9489	E1	31
N Male	90º	PE9565	A2	31
Reverse Polarity TNC Female		PE91087	A6	44
SC Male		PE9568	A7	33
SMA Female		PE9073	B4	38
SMA Female		PE9494	C4	38
SMA Male		PE9072	E4	36
SMA Male		PE9493	A5	36
SMB Jack		PE9132	C3	41
SMB Plug		PE9135	E2	41
SMC Jack		PE9138	D6	41
SMC Plug		PE9139	E5	41
SSMA Female		PE9191	B5	42
SSMA Male		PE9213	D4	42
SSMB Jack		PE9392	C6	42
SSMB Plug		PE9393	A6	42
TNC Female		PE9098	E3	44
TNC Male		PE91449	E7	43
UHF Female		PE91329	D1	45
UHF Male		PE9201	D7	44
BNC Triax Female To:				
BNC Male		PE91104	D1	26
BNC Triax In-Series:				
Female to Female		PE91107	C5	48
Female to Female	(B) (PM)	PE91105	D5	48
Male to Female		PE91106	B5	48
C Female To:				
BNC Female		PE9537	E3	26
BNC Female	(B) (PM)	PE9204	A4	26
BNC Male		PE9109	A2	26
GR874 Sexless		PE9301	A3	27
HN Male		PE9296	A6	27
N Female		PE9539	C4	32
N Male		PE91446	B3	31
N Male	90º	PE9239	C3	31
TNC Male		PE9562	C1	44
C In-Series:				
Female to Female		PE9208	B6	26
Female to Female		PE9294	C6	26
Female to Female	(B) (PM)	PE9186	D6	26
Female to Male		PE9207	A6	26
Male to Female	90º	PE9293	E5	26
Male to Male		PE9300	D5	26
C Male To:				
BNC Female		PE9087	D3	26
BNC Male		PE9536	E1	26
HN Female		PE9212	E6	27
HN Male		PE9579	E5	27
N Female		PE9295	B4	32
N Male		PE9538	A3	31
TNC Female		PE9564	B4	44
Double Banana Binding Post Jack To:				
BNC Female		PE9013	E4	48
BNC Male		PE9011	C1	26
Double Banana Plug To:				
BNC Female		PE9008	A4	48
BNC Male		PE9009	E3	48
D-Sub In-Series:				
Plug to Plug		PE9688	A7	26
Plug to Receptacle		PE9687	B7	26
Receptacle to Receptacle		PE9689	C7	26
FME In-Series:				
Plug to Plug		PE9696	E7	26
FME Jack To:				
BNC Female		PE9712	E1	27
BNC Male		PE9711	D1	27
Mini UHF Female		PE9710	D1	29
Mini UHF Male		PE9709	B1	29
SMA Female		PE9708	A6	38
SMA Male		PE9707	E5	36
TNC Female		PE9714	C4	44
TNC Male		PE9713	A2	44
FME Plug To:				
BNC Male		PE9697	B1	27
BNC Male	90º	PE9698	C1	27
Mini UHF Male		PE9705	E7	28
Mini UHF Male	90º	PE9706	A1	29
N Male		PE9704	E3	31
SMA Female		PE9703	E5	38
TNC Male		PE9699	D1	44
TNC Male	90º	PE9700	E1	44
UHF Male		PE9701	B1	45
Full Detent Mini SMP Male To:				
2.4mm Female		PE91122	C5	19
2.4mm Male		PE91121	D3	19
2.92mm Female		PE91127	B1	21
SMA Female		PE91299	B7	38
SMA Female		PE91129	D7	38
SMA Male		PE91302	A7	36
SMA Male	(P)	PE91052	C7	36
Full Detent SMP Male To:				
SMA Female		PE91305	D5	39
SMA Female	(P)	PE91056	D6	39
SMA Female	(B) (PM)	PE91054	B7	39
SMA Female	(P) (PM)	PE91058	D7	39
SMA Male		PE91309	D4	37
SMA Male	(P)	PE91063	B5	37
GR874 In-Series:				
Sexless to Sexless	90º	PE9286	B2	27
Sexless to Sexless		PE9285	C2	27
GR874 Sexless To:				
BNC Male		PE9223	E2	27
C Female		PE9301	A3	27
HN Female		PE9387	A7	27
HN Male		PE9386	B6	27
N Female		PE9258	E4	32
N Male		PE9257	A4	31
SMA Female		PE9260	B6	38
SMA Male		PE9259	A6	36
HN Female To:				
7/16 DIN Male		PE9558	E2	24
BNC Male		PE9129	D6	27
C Male		PE9212	E6	27
GR874 Sexless		PE9387	A7	27
LC Male		PE9181	B1	28
N Female		PE9360	B5	32
N Female	(PM)	PE9553	C5	32
N Male		PE9125	C4	31
SMA Female		PE9255	D6	38
SMA Male		PE9256	C6	36
HN In-Series:				
Female to Female		PE9580	D4	27
Female to Female		PE9574	E4	27
Female to Female	(B) (PM)	PE9193	A5	27
Female to Male		PE9575	C4	27
Male to Female		PE9576	E3	27
Male to Female	90º	PE9205	A4	27
Male to Female		PE9578	B4	27
Male to Male		PE9210	C3	27
Male to Male	90º	PE9577	D3	27
HN Male To:				
7/16 DIN Female		PE9559	C6	24
BNC Female		PE9126	D5	27
BNC Male		PE9567	C5	27
C Female		PE9296	A6	27
C Male		PE9579	E5	27
GR874 Sexless		PE9386	B6	27
LC Female		PE9413	C1	28
MHV Female		PE9264	C6	27
N Female		PE9194	A5	32
N Male		PE9554	B4	31
SMA Female		PE9253	C6	38
SMA Male		PE91448	B6	36
TNC Male		PE9563	B2	44
LC Female To:				
HN Male		PE9413	C1	28
N Female		PE9298	E5	32
N Male		PE9299	D4	31
LC In-Series:				
Female to Female		PE9419	E7	27
Male to Female	90º	PE9398	D7	27
Male to Male		PE9569	C7	27
LC Male To:				
HN Female		PE9181	B1	28
N Female		PE9237	D5	32
Limited Detent SMP Male To:				
SMA Female		PE91306	E5	39
SMA Female	(P)	PE91050	C6	39
SMA Female	(P)	PE9512	E6	39
SMA Female		PE9778	A7	39
SMA Female	(P) (PM)	PE91066	A1	40
SMA Male		PE91310	E4	37
SMA Male	(P)	PE9511	C5	37
TNC Female	(B)	PE91073	C5	44
MCX In-Series:				
Jack to Jack		PE9524	A2	28
Jack to Jack	(B)	PE9474	B2	28
Plug to Jack		PE9479	E1	28
MCX Jack To:				
BNC Female		PE9466	B3	28
BNC Female	(B) (PM)	PE9520	C3	28
BNC Male		PE9468	A3	28
MMCX Jack		PE9526	A4	29
MMCX Plug		PE9525	B3	29
N Female		PE9462	B6	32
N Male		PE9464	A5	31
SMA Female		PE9470	A7	38
SMA Male		PE9472	E6	36
TNC Female		PE9544	E4	44
TNC Female	(B) (PM)	PE9521	A5	44
TNC Male		PE9542	D2	44
MCX Plug To:				
BNC Female		PE9467	E2	28
BNC Male		PE9469	D2	28
MMCX Jack		PE9528	E3	29
MMCX Plug		PE9527	A3	29
N Female		PE9463	A6	32
N Male		PE9465	E4	31

Feature: (B) Bulkhead Mount / (H) Hermetically Sealed / (I) Isolated Sealed / (LP) Low PIM / (P) Precision / (PM) Panel Mount / (PO) Push On / (QD) Quick Disconnect / (R) Radius Right Angle / (RU) Ruggedized / (SO) Snap-On

Adapter Locator

Connector Type	Feature	Model No.	C/R	Page
SMA Female		PE9471	E6	38
SMA Male		PE9473	D6	36
TNC Female		PE9545	D4	44
TNC Male		PE9543	C2	44
MHV Female To:				
BNC Male		PE9406	D2	26
HN Male		PE9264	C6	27
SHV Jack		PE9339	D5	28
SHV Plug		PE9265	C5	28
MHV In-Series:				
Female to Female		PE9267	C4	28
Female to Female	(B)	PE9268	D4	28
Female to Male		PE9211	B4	28
Male to Female		PE9297	E3	28
Male to Female	90º	PE9266	A4	28
MHV Male To:				
SHV Jack		PE9335	B5	28
SHV Plug		PE9340	A5	28
Mini SMP Female To:				
2.4mm Female		PE91123	D5	19
2.92mm Female		PE9782	D1	21
2.92mm Male		PE91126	D5	20
SMA Female		PE91301	E7	38
SMA Female	(P)	PE91051	A1	39
SMA Male		PE91304	D7	36
SMA Male	(P)	PE91103	E7	36
Mini SMP In-Series:				
Female to Female		PE9780	A6	28
Female to Female		PE91069	B6	28
Mini SMP Male To:				
2.92mm Male		PE91124	B5	20
Mini UHF Female To:				
BNC Male		PE9341	C1	29
FME Jack		PE9710	D1	29
N Male		PE9064	B5	31
TNC Male		PE9345	E2	44
UHF Male		PE9348	C1	45
Mini UHF In-Series:				
Female to Female		PE9343	A7	28
Female to Female		PE9066	B7	28
Female to Male		PE9065	E6	28
Male to Female	90º	PE9347	D6	28
Mini UHF Male To:				
BNC Female		PE9342	D7	28
FME Jack		PE9709	B1	29
FME Plug		PE9705	E7	28
FME Plug	90º	PE9706	A1	29
N Female		PE9183	C6	32
TNC Female		PE9346	B5	44
UHF Female		PE91447	B2	45
MMBX In-Series:				
Plug to Plug	(SO)	PE91370	C4	29
Plug to Plug		PE91371	D4	29
Plug to Plug	(SO)	PE91372	E4	29
Plug to Plug	(SO)	PE91373	A5	29
MMCX In-Series:				
Jack to Jack		PE9523	B2	29
Jack to Jack	(B) (PM)	PE9522	C2	29
Plug to Jack		PE9480	A2	29
MMCX Jack To:				
BNC Female		PE9516	D3	29
BNC Male		PE9518	C3	29
MCX Jack		PE9526	A4	29
MCX Plug		PE9528	E3	29
SMA Female		PE9477	C1	39
SMA Male		PE9478	B1	37
MMCX Plug To:				
BNC Male		PE9517	E2	29
MCX Jack		PE9525	B3	29
MCX Plug		PE9527	A3	29
SMA Female		PE9475	B1	39
SMA Male		PE9476	A1	37
N Female To:				
1.85mm Female		PE9721	B7	18
1.85mm Male		PE9719	E5	18
2.4mm Female	(P)	PE9502	A6	19
2.4mm Male	(P)	PE9501	A4	19
2.92mm Female	(P)	PE9664	A2	21
2.92mm Male	(P)	PE9662	A6	20
3.5mm Female	(P)	PE9323	E1	22
3.5mm Male	(P)	PE9324	E6	21
4.1/9.5 Mini DIN Female		PE91218	C6	22
4.1/9.5 Mini DIN Female		PE91255	D6	22
4.1/9.5 Mini DIN Female	(LP)	PE91095	E6	22
4.1/9.5 Mini DIN Male		PE91217	B5	22
4.1/9.5 Mini DIN Male		PE91254	C5	22
4.1/9.5 Mini DIN Male	(LP)	PE91093	D5	22
4.3-10 Female	(LP)	PE91475	E3	23
4.3-10 Male	(LP)	PE91474	B2	23
4.3-10 Male	(LP)	PE91477	C2	23
4.3-10 Male	(LP) 90º	PE91483	E2	23
4.3-10 Male	(LP)	PE91389	A3	23
7/16 DIN Female	(LP)	PE91033	A2	32
7/16 DIN Female	(LP)	PE9180	B2	32
7/16 DIN Female		PE91213	A7	24
7/16 DIN Female		PE91250	B7	24
7/16 DIN Female	(B)	PE91215	C7	24

Connector Type	Feature	Model No.	C/R	Page
7/16 DIN Female	(B)	PE91252	D7	24
7/16 DIN Male	(LP)	PE91031	E1	32
7/16 DIN Male		PE91212	C3	24
7/16 DIN Male		PE91249	D3	24
75 Ohm F Male		PE9389	D4	32
7mm Sexless	(P)	PE9216	D1	32
BNC Female		PE9206	B3	32
BNC Female	(P)	PE9492	C3	32
BNC Female	(B) (PM)	PE9261	D3	32
BNC Female	(PM)	PE9238	E3	32
BNC Female	(B) (PM)	PE9540	A4	32
BNC Male		PE9005	C2	32
BNC Male	(P)	PE9490	D2	32
BNC Male	90º	PE9566	E2	32
BNC Male	(PM)	PE9123	A3	32
C Female		PE9539	C4	32
C Male		PE9295	B4	32
GR874 Sexless		PE9258	E4	32
HN Female		PE9360	B5	32
HN Female	(PM)	PE9553	C5	32
HN Male		PE9194	A5	32
LC Female		PE9298	E5	32
LC Male		PE9237	D5	32
MCX Jack		PE9462	B6	32
MCX Plug		PE9463	A6	32
Mini UHF Male		PE9183	C6	32
QD 4.3-10 Female	(LP) (QD)	PE91482	A4	23
QD 4.3-10 Male	(LP) (QD)	PE91478	D2	23
Reverse Polarity SMA Male		PE9732	E5	40
Reverse Polarity TNC Male		PE9731	C3	33
SC Female		PE9292	E6	32
SC Male		PE9277	D6	32
SMA Female		PE9083	A3	39
SMA Female	(P)	PE9432	B3	39
SMA Female	(B)	PE9252	C3	39
SMA Female	(B) (P)	PE9486	D3	39
SMA Female	(PM)	PE9104	E3	39
SMA Female	(P) (PM)	PE9434	A4	39
SMA Female	(B)	PE9408	B4	39
SMA Female	(B) (P) (PM)	PE9435	C4	39
SMA Male	(LP)	PE91178	A7	32
SMA Male		PE9082	C2	37
SMA Male	(P)	PE9433	D2	37
SMA Male	(B) (P)	PE9487	E2	37
SMA Male	(PM)	PE9105	A3	37
SMA Male	(P) (PM)	PE9497	B3	37
SMA Male	(B) (P)	PE9488	C3	37
SMB Jack		PE9315	C7	32
SMB Plug		PE9316	B7	32
SMC Jack		PE9319	E7	32
SMC Plug		PE9320	D7	32
SSMA Female		PE9354	D5	42
TNC Female		PE9131	D1	33
TNC Female	(P)	PE9449	E1	33
TNC Female	(PM)	PE9552	A2	33
TNC Female	(B)	PE9482	B2	33
TNC Female	(P) (PM)	PE9450	C2	33
TNC Male		PE9089	A1	33
TNC Male	(P)	PE91506	B1	33
TNC Male	90º	PE9263	C1	33
UHF Female		PE9385	E2	33
UHF Male		PE9112	D2	33
N In-Series:				
Female to Female		PE91200	D2	30
Female to Female		PE91237	E2	30
Female to Female		PE9006	A3	30
Female to Female	(LP)	PE91140	B3	30
Female to Female		PE91141	C3	30
Female to Female	(P)	PE91530	D3	30
Female to Female	90º	PE9359	E3	30
Female to Female		PE9101	A4	30
Female to Female		PE9548	B4	30
Female to Female	(B)	PE9128	C4	30
Female to Female	(B)	PE9383	D4	30
Female to Female	(B) 90º	PE9541	E4	30
Female to Female	(PM)	PE9173	A5	30
Female to Female	(P) (PM)	PE9429	B5	30
Female to Female	(B)	PE91201	C5	30
Female to Female	(B)	PE91238	D5	30
Female to Female	(B) (LP)	PE91179	E5	30
Female to Female	(B) (P)	PE9500	A6	30
Female to Female	(B)	PE9382	B6	30
Female to Male		PE9350	B2	30
Female to Male		PE9102	C2	30
Female to Male		PE9770	E6	30
Male to Female		PE91199	E6	29
Male to Female		PE91236	A7	29
Male to Female	(LP)	PE91040	B7	29
Male to Female	(PO)	PE91114	C7	29
Male to Female	(P)	PE91531	D7	29
Male to Female		PE9311	E7	29
Male to Female		PE9349	A1	30
Male to Female	(QD)	PE9547	B1	30
Male to Female	(P) (R)	PE91350	C1	30
Male to Female	90º	PE9086	D1	30
Male to Female		PE9481	E1	30
Male to Female	(B)	PE9595	A2	30
Male to Female		PE9771	D6	30
Male to Male		PE91198	C5	29

Connector Type	Feature	Model No.	C/R	Page
Male to Male		PE91235	D5	29
Male to Male		PE9007	E5	29
Male to Male	(LP)	PE91034	A6	29
Male to Male	(P)	PE91532	B6	29
Male to Male	90º	PE9198	C6	29
Male to Male		PE9390	D6	29
N Male To:				
1.85mm Female		PE9720	A7	18
1.85mm Male		PE9718	D5	18
2.4mm Female	(P)	PE9503	E5	19
2.4mm Male	(P)	PE9504	E3	19
2.92mm Female	(P)	PE9663	E1	21
2.92mm Male	(P)	PE9661	E5	20
3.5mm Female	(P)	PE9321	D1	22
3.5mm Male	(P)	PE9322	D6	21
4.1/9.5 Mini DIN Female		PE91219	E5	22
4.1/9.5 Mini DIN Female		PE91256	A6	22
4.1/9.5 Mini DIN Female	(LP)	PE91094	B6	22
4.1/9.5 Mini DIN Male		PE91216	E4	22
4.1/9.5 Mini DIN Male	(LP)	PE91092	A5	22
4.3-10 Female	(LP)	PE91388	D7	30
4.3-10 Female	(LP)	PE91479	C3	23
4.3-10 Male	(LP)	PE91476	E1	23
7/16 DIN Female	(LP)	PE91032	B1	31
7/16 DIN Female		PE91134	C1	31
7/16 DIN Female		PE91214	D6	24
7/16 DIN Female		PE91251	E6	24
7/16 DIN Male	(LP)	PE91030	E7	30
7/16 DIN Male		PE9535	A1	31
7/16 DIN Male		PE91211	A3	24
7/16 DIN Male		PE91248	B3	24
75 Ohm F Female		PE9155	D3	31
7mm Sexless	(P)	PE9217	C7	30
BNC Female		PE9002	B2	31
BNC Female	(P)	PE9491	C2	31
BNC Female	90º	PE9278	D2	31
BNC Female	(PM)	PE9388	E2	31
BNC Male		PE9127	D1	31
BNC Male	(P)	PE9489	E1	31
BNC Male	90º	PE9565	A2	31
C Female		PE91446	B3	31
C Female	90º	PE9239	C3	31
C Male		PE9538	A3	31
FME Plug		PE9704	E3	31
GR874 Sexless		PE9257	A4	31
HN Female		PE9125	C4	31
HN Male		PE9554	B4	31
LC Female		PE9299	D4	31
MCX Jack		PE9464	A5	31
MCX Plug		PE9465	E4	31
Mini UHF Female		PE9064	B5	31
QD 4.3-10 Female	(LP) (QD)	PE91481	D3	23
QD 4.3-10 Male	(LP) (QD)	PE91480	A2	23
QMA Female		PE9787	C5	31
Reverse Polarity SMA Female		PE9733	C6	40
Reverse Polarity TNC Female		PE9730	B3	33
SC Female		PE9196	E5	31
SC Male		PE9570	D5	31
SMA Female	(LP)	PE91177	A6	31
SMA Female	(P)	PE91339	B6	31
SMA Female		PE9081	A2	39
SMA Female	(B)	PE9551	C2	39
SMA Female	(PM)	PE9275	D2	39
SMA Female	(P) (PM)	PE9498	E2	39
SMA Male		PE9080	E1	37
SMA Male	(P)	PE9431	A2	37
SMA Male	(P) (PM)	PE9499	B2	37
SMB Jack		PE9313	D6	31
SMB Plug		PE9314	C6	31
SMC Jack		PE9317	A7	31
SMC Plug		PE9318	E6	31
SSMA Female		PE9352	C5	42
SSMA Male		PE9351	A5	42
TNC Female		PE9090	D7	31
TNC Female	90º	PE9550	E7	31
TNC Female		PE91537	A1	32
TNC Male		PE9130	B7	31
TNC Male	(P)	PE9446	C7	31
UHF Female		PE9111	C1	32
UHF Male		PE9113	B1	32
Push-On SMA Male To:				
SMA Female	(PO)	PE91336	D3	37
Push-On SMP Female To:				
Snap-On MMBX Plug	(PO) (SO)	PE91364	D2	42
QD 4.3-10 Female To:				
7/16 DIN Female	(LP) (QD)	PE91473	B6	24
N Female	(LP) (QD)	PE91482	A4	23
N Male	(LP) (QD)	PE91481	D3	23
QD 4.3-10 Male To:				
7/16 DIN Female	(LP) (QD)	PE91472	D5	24
N Female	(LP) (QD)	PE91478	D2	23
N Male	(LP) (QD)	PE91480	A2	23
QD N Male To:				
SMA Female	(QD)	PE9684	B2	39
QMA Female To:				
N Male		PE9787	C5	31
QMA In-Series:				
Female to Female	(SO)	PE91343	B4	33

Feature: (B) Bulkhead Mount / (H) Hermetically Sealed / (I) Isolated Sealed / (LP) Low PIM / (P) Precision / (PM) Panel Mount / (PO) Push On / (QD) Quick Disconnect / (R) Radius Right Angle / (RU) Ruggedized / (SO) Snap-On

Adapter Locator

Connector Type	Feature	Model No.	C/R	Page
Male to Female	(SO)	PE91342	A4	33
Male to Male	(SO)	PE91341	E3	33
QMA Male To:				
SMA Female		PE9786	D4	39
Reverse Polarity MCX Plug To:				
SMA Male		PE9581	A5	40
Reverse Polarity N In-Series:				
Female to Female		PE9773	A7	30
Reverse Polarity SMA Female To:				
N Male		PE9733	C6	40
Reverse Polarity TNC Female		PE9606	D7	40
Reverse Polarity TNC Male		PE9607	C7	40
TNC Female		PE9599	E6	40
TNC Male		PE9598	D6	40
Reverse Polarity SMA In-Series:				
Female to Female		PE91262	D7	35
Female to Female		PE91334	E7	35
Female to Female	(B) (PM)	PE9593	A1	36
Female to Female	(PM)	PE91270	B1	36
Female to Female	(PM)	PE91269	C1	36
Male to Female	(QD)	PE91267	B6	35
Male to Female	90º	PE91263	C6	35
Male to Female	(QD)	PE91268	A7	35
Male to Female		PE91331	B7	35
Male to Female	90º	PE9594	C7	35
Male to Male	(QD)	PE91266	A6	35
Male to Male		PE91261	D6	35
Male to Male		PE91330	E6	35
Reverse Polarity SMA Male To:				
N Female		PE9732	E5	40
Reverse Polarity TNC Female		PE9604	B7	40
Reverse Polarity TNC Male		PE9605	A7	40
TNC Female		PE9596	B6	40
TNC Male		PE9597	A6	40
Reverse Polarity TNC Female To:				
BNC Male		PE91087	A6	44
N Male		PE9730	B3	33
Reverse Polarity SMA Female		PE9606	D7	40
Reverse Polarity SMA Male		PE9604	B7	40
SMA Female		PE9603	D5	40
SMA Male		PE9600	B5	40
Reverse Polarity TNC In-Series:				
Male to Female	90º	PE9918	A7	43
Reverse Polarity TNC Male To:				
N Female		PE9731	C3	33
Reverse Polarity SMA Female		PE9607	C7	40
Reverse Polarity SMA Male		PE9605	A7	40
SMA Female		PE9602	C5	40
SC Female To:				
7/16 DIN Male		PE91444	E3	24
BNC Female		PE9571	B7	33
N Female		PE9292	E6	32
N Male		PE9196	E5	31
SC In-Series:				
Female to Female		PE9404	C6	33
Female to Female	(B)	PE9573	D6	33
Female to Male		PE9225	B6	33
Male to Female		PE9572	E5	33
Male to Female	90º	PE9405	A6	33
Male to Male		PE9403	D5	33
SC Male To:				
BNC Male		PE9568	A7	33
N Female		PE9277	D6	32
N Male		PE9570	D5	31
SHV In-Series:				
Jack to Jack		PE9337	B1	34
Jack to Jack	(B)	PE9336	C1	34
Jack to Plug		PE9249	A1	34
Plug to Jack		PE9749	D7	33
Plug to Jack	90º	PE9338	E7	33
SHV Jack To:				
MHV Female		PE9339	D5	28
MHV Male		PE9335	B5	28
SHV Plug To:				
MHV Female		PE9265	C5	28
MHV Male		PE9340	A5	28
Slide-On BMA Jack To:				
SMA Female		PE91400	C4	25
SMA Female	(PM)	PE91399	D4	25
SMA Male		PE91397	B4	25
Slide-On BMA Plug To:				
SMA Female		PE91398	E3	25
SMA Female	(B)	PE91402	A4	25
SMA Male		PE91396	C3	25
SMA Male	(B)	PE91401	D3	25
SMA Female To:				
1.0/2.3 Jack		PE9693	C1	38
1.0/2.3 Plug		PE9691	B1	38
1.85mm Female		PE9729	E1	38
1.85mm Male		PE9726	D1	38
2.4mm Female	(P)	PE9656	B2	38
2.4mm Male		PE9655	A2	38
2.4mm NMD Female	(RU)	PE91146	A7	19
2.92mm Female	(P)	PE91011	D2	38
2.92mm Male	(P)	PE91009	C2	38
3.5mm Female		PE9725	A3	38
3.5mm Male		PE9724	E2	38

Connector Type	Feature	Model No.	C/R	Page
3.5mm NMD Female	(RU)	PE91147	C2	22
4.3-10 Male	(LP)	PE91484	B3	23
7/16 DIN Female	(LP)	PE91042	A4	38
7/16 DIN Male	(LP)	PE91036	D3	38
7/16 DIN Male		PE91175	E3	38
75 Ohm F Female		PE91002	D5	38
75 Ohm F Male		PE91045	C5	38
7mm Sexless	(P)	PE9214	B3	38
7mm Sexless	(P) (PM)	PE9327	C3	38
BNC Female		PE9075	D4	38
BNC Female		PE9496	E4	38
BNC Female	(B)	PE9185	A5	38
BNC Female	(B)	PE9407	B5	38
BNC Male		PE9073	B4	38
BNC Male		PE9494	C4	38
FME Jack		PE9708	A6	38
FME Plug		PE9703	E5	38
Full Detent Mini SMP Male		PE91299	B7	38
Full Detent Mini SMP Male		PE91129	D7	38
Full Detent SMP Male		PE91305	D5	39
Full Detent SMP Male	(P)	PE91056	D6	39
Full Detent SMP Male	(B) (PM)	PE91054	B7	39
Full Detent SMP Male	(P) (PM)	PE91058	D7	39
GR874 Sexless		PE9260	B6	38
HN Female		PE9255	D6	38
HN Male		PE9253	C6	38
Limited Detent SMP Male		PE91306	E5	39
Limited Detent SMP Male	(P)	PE91050	C6	39
Limited Detent SMP Male	(P)	PE9512	E6	39
Limited Detent SMP Male		PE9778	A7	39
Limited Detent SMP Male	(P) (PM)	PE91066	A1	40
MCX Jack		PE9470	A7	38
MCX Plug		PE9471	E6	38
Mini SMP Female		PE91301	E7	38
Mini SMP Female	(P)	PE91051	A1	39
MMCX Jack		PE9477	C1	39
MMCX Plug		PE9475	B1	39
N Female		PE9083	A3	39
N Female	(P)	PE9432	B3	39
N Female	(B)	PE9252	C3	39
N Female	(B) (P)	PE9486	D3	39
N Female	(PM)	PE9104	E3	39
N Female	(P) (PM)	PE9434	A4	39
N Female	(B)	PE9408	B4	39
N Female	(B) (P) (PM)	PE9435	C4	39
N Male		PE9081	A2	39
N Male	(B)	PE9551	C2	39
N Male	(PM)	PE9275	D2	39
N Male	(P) (PM)	PE9498	E2	39
N Male	(LP)	PE91177	A6	31
N Male	(P)	PE91339	B6	31
Push-On SMA Male	(PO)	PE91336	D3	37
QD N Male	(QD)	PE9684	B2	39
QMA Male		PE9786	D4	39
Reverse Polarity TNC Female		PE9603	D5	40
Reverse Polarity TNC Male		PE9602	C5	40
Slide-On BMA Jack		PE91400	C4	25
Slide-On BMA Jack	(PM)	PE91399	D4	25
Slide-On BMA Plug		PE91398	E3	25
Slide-On BMA Plug	(B)	PE91402	A4	25
SMB Jack		PE9143	A5	39
SMB Plug		PE9142	E4	39
SMC Jack		PE9147	C5	39
SMC Plug		PE9146	B5	39
Smooth Bore Mini SMP Male		PE91300	C7	38
Smooth Bore SMP Male		PE91307	A6	39
Smooth Bore SMP Male	(P)	PE91049	B6	39
Smooth Bore SMP Male	(P) (PM)	PE91061	E7	39
SMP Female		PE91308	C1	40
SMP Female	(P)	PE91064	D1	40
SMP Female	(P)	PE9779	E1	40
SMP Male	(P) (PM)	PE91057	C7	39
SMP Male	(P) (PM)	PE91059	B1	40
Snap-On MMBX Jack	(SO)	PE91363	E1	39
Snap-On MMBX Plug	(SO)	PE91361	D1	39
Snap-On QMA Male	(SO)	PE91345	E4	33
SSMA Female		PE9399	B2	40
SSMA Male		PE9188	A2	40
SSMB Plug		PE9402	C2	40
SSMC Jack		PE91433	E2	40
SSMC Plug		PE91380	D2	40
TNC Female		PE9079	C3	40
TNC Female		PE9442	D3	40
TNC Female	(B) (PM)	PE9251	E3	40
TNC Female	(PM)	PE9276	A4	40
TNC Male		PE9077	A3	40
TNC Male		PE9440	B3	40
UHF Male		PE9415	B4	40
UMCX Jack		PE91006	D4	40
UMCX Plug		PE91005	C4	40
SMA In-Series:				
Female to Female		PE9070	B7	34
Female to Female		PE9380	C7	34
Female to Female	(P)	PE9507	D7	34
Female to Female	(P)	PE9695	E7	34

Connector Type	Feature	Model No.	C/R	Page
Female to Female	(R)	PE91494	A1	35
Female to Female	(R)	PE91495	B1	35
Female to Female	90º (P)	PE91153	C1	35
Female to Female	90º	PE9485	D1	35
Female to Female		PE9246	E1	35
Female to Female	(B) (PM)	PE9014	A2	35
Female to Female	(B)	PE91258	B2	35
Female to Female	(B) (PM)	PE9508	C2	35
Female to Female	(B) (P) (PM)	PE9620	D2	35
Female to Female	(H) (B)	PE91393	E2	35
Female to Female	(B)	PE9184	A3	35
Female to Female	(B)	PE9067	B3	35
Female to Female	(PM)	PE9312	C3	35
Female to Female	(PM)	PE9670	D3	35
Female to Female	(B)	PE9184NH	E3	35
Female to Female	(PM)	PE91290	A4	35
Female to Female	(P)	PE91549	B4	35
Female to Female	90º	PE91176	C4	35
Female to Female		PE91260	E5	35
Female to Male		PE9182	A7	34
Female to Male		PE9533	D5	35
Female to Male		PE9683	A2	36
Male to Female		PE9103	E3	34
Male to Female	(P)	PE9506	A4	34
Male to Female	(QD)	PE9546	B4	34
Male to Female	(P)	PE9694	C4	34
Male to Female	(P) (QD)	PE9774	D4	34
Male to Female	(R)	PE91492	E4	34
Male to Female	(R)	PE91493	A5	34
Male to Female	(R)	PE91155	B5	34
Male to Female	(R)	PE91222	C5	34
Male to Female	90º	PE9068	D5	34
Male to Female	(P) 45º	PE91332	E5	34
Male to Female		PE9247	A6	34
Male to Female	(B)	PE9621	B6	34
Male to Female	(PM)	PE91453	C6	34
Male to Female	(B) (PO)	PE91321	D6	34
Male to Female	(P) 90º	PE91504	E6	34
Male to Female	(QD)	PE91265	A5	35
Male to Female		PE9534	B5	35
Male to Female	90º	PE91264	C5	35
Male to Female		PE9682	E1	36
Male to Male		PE91135	E1	34
Male to Male	(P)	PE9505	A2	34
Male to Male	(R)	PE91496	B2	34
Male to Male	(R)	PE91497	C2	34
Male to Male	90º	PE9418	D2	34
Male to Male		PE9379	E2	34
Male to Male	(P) 90º	PE91151	A3	34
Male to Male	(R) 90º	PE9642	B3	34
Male to Male	(PM)	PE9669	C3	34
Male to Male		PE91535	D3	34
Male to Male		PE91259	E4	35
SMA Male To:				
1.0/2.3 Jack		PE9690	D2	36
1.0/2.3 Plug		PE9692	C2	36
1.85mm Female		PE9728	A3	36
1.85mm Male		PE9727	E2	36
2.4mm Female	(P)	PE9654	C3	36
2.4mm Male	(P)	PE9653	B3	36
2.92mm Female	(P)	PE91008	E3	36
2.92mm Male	(P)	PE91010	D3	36
3.5mm Female		PE91536	B4	36
3.5mm Male		PE9722	A4	36
7/16 DIN Female		PE9411	D4	36
75 Ohm F Female		PE91003	D5	36
7mm Sexless	(P)	PE9215	C4	36
BNC Female		PE9074	B5	36
BNC Female		PE9495	C5	36
BNC Male		PE9072	E4	36
BNC Male		PE9493	A5	36
FME Jack		PE9707	E5	36
Full Detent Mini SMP Male		PE91302	A7	36
Full Detent Mini SMP Male	(P)	PE91052	C7	36
Full Detent SMP Male		PE91309	D4	37
Full Detent SMP Male	(P)	PE91063	B5	37
GR874 Sexless		PE9259	A6	36
HN Female		PE9256	C6	36
HN Male		PE91448	B6	36
Limited Detent SMP Male		PE91310	E4	37
Limited Detent SMP Male	(P)	PE9511	C5	37
MCX Jack		PE9472	E6	36
MCX Plug		PE9473	D6	36
Mini SMP Female		PE91304	D7	36
Mini SMP Female	(P)	PE91103	E7	36
MMCX Jack		PE9478	B1	37
MMCX Plug		PE9476	A1	37
N Female		PE9082	C2	37
N Female	(P)	PE9433	D2	37
N Female	(B) (P)	PE9487	E2	37
N Female	(PM)	PE9105	A3	37
N Female	(P) (PM)	PE9497	B3	37
N Female	(B) (P)	PE9488	C3	37
N Female	(LP)	PE91178	A7	32
N Male		PE9080	E1	37
N Male	(P)	PE9431	A2	37

Feature: (B) Bulkhead Mount / (H) Hermetically Sealed / (I) Isolated Sealed / (LP) Low PIM / (P) Precision / (PM) Panel Mount / (PO) Push On / (QD) Quick Disconnect / (R) Radius Right Angle / (RU) Ruggedized / (SO) Snap-On

Adapter Locator

Connector Type	Feature	Model No.	C/R	Page
N Male	(P) (PM)	PE9499	B2	37
Reverse Polarity MCX Plug		PE9581	A5	40
Reverse Polarity TNC Female		PE9600	B5	40
Slide-On BMA Jack		PE91397	B4	25
Slide-On BMA Plug		PE91396	C3	25
Slide-On BMA Plug	(B)	PE91401	D3	25
SMB Jack		PE9145	A4	37
SMB Plug		PE9144	E3	37
SMC Jack		PE9149	C4	37
SMC Plug		PE9148	B4	37
Smooth Bore Mini SMP Male		PE91303	B7	36
Smooth Bore SMP Male		PE91311	A5	37
SMP Female		PE91312	D5	37
SMP Female	(P)	PE91062	E5	37
SMP Female	(P)	PE9513	A6	37
Snap-On MMBX Jack	(SO)	PE91362	D1	37
Snap-On MMBX Plug	(SO)	PE91360	C1	37
Snap-On QMA Female	(SO)	PE91346	A5	33
SSMA Female		PE9063	C6	37
SSMA Male		PE9187	B6	37
SSMB Jack		PE9401	D6	37
TNC Female		PE9078	B7	37
TNC Female		PE91507	C7	37
TNC Female	(PM)	PE9384	D7	37
TNC Male		PE9076	E6	37
TNC Male		PE9439	A7	37
UHF Female		PE9400	E7	37
UMCX Jack		PE91007	A1	38
SMB In-Series:				
Jack to Jack		PE9116	A2	41
Jack to Jack		PE9302	B2	41
Jack to Jack	(B) (PM)	PE9122	C2	41
Jack to Plug		PE9243	E1	41
Plug to Jack		PE9120	C1	41
Plug to Jack		PE9309	D1	41
Plug to Plug		PE9118	A1	41
Plug to Plug		PE9310	B1	41
SMB Jack To:				
BNC Female		PE9136	D3	41
BNC Female	(B)	PE9240	E3	41
BNC Male		PE9132	C3	41
N Female		PE9315	C7	32
N Male		PE9313	D6	31
SMA Female		PE9143	A5	39
SMA Male		PE9145	A4	37
SMC Jack		PE9283	C7	41
SMC Plug		PE9284	C6	41
SMB Plug To:				
BNC Female		PE9137	A3	41
BNC Female	(B) (PM)	PE9241	B3	41
BNC Male		PE9135	E2	41
N Female		PE9316	B7	32
N Male		PE9314	C6	31
SMA Female		PE9142	E4	39
SMA Male		PE9144	E3	37
SMC Jack		PE9282	B7	41
SMC Plug		PE9281	B6	41
SMC In-Series:				
Jack to Jack		PE9304	B5	41
Jack to Jack	(B) (PM)	PE91403	C5	41
Jack to Plug		PE9242	A5	41
Plug to Jack		PE9119	D4	41
Plug to Jack	90º	PE9303	E4	41
Plug to Plug		PE9117	B4	41
Plug to Plug		PE9305	C4	41
SMC Jack To:				
BNC Female		PE9140	E6	41
BNC Female	(B)	PE9108	A7	41
BNC Male		PE9138	D6	41
N Female		PE9319	E7	32
N Male		PE9317	A7	31
SMA Female		PE9147	C5	39
SMA Male		PE9149	C4	37
SMB Jack		PE9283	C7	41
SMB Plug		PE9282	B7	41
TNC Male		PE9226	A3	44
SMC Plug To:				
BNC Female		PE9141	A6	41
BNC Male		PE9139	E5	41
N Female		PE9320	D7	32
N Male		PE9318	E6	31
SMA Female		PE9146	B5	39
SMA Male		PE9148	B4	37
SMB Jack		PE9284	C6	41
SMB Plug		PE9281	B6	41
Smooth Bore Mini SMP Male To:				
2.92mm Female		PE91128	C1	21
2.92mm Male		PE91125	C5	20
SMA Female		PE91300	C7	38
SMA Male		PE91303	B7	36
Smooth Bore SMP Male To:				
SMA Female		PE91307	A6	39
SMA Female	(P)	PE91049	B6	39
SMA Female	(P) (PM)	PE91061	E7	39
SMA Male		PE91311	A5	37
SMP Female To:				
2.4mm Female		PE91055	C6	19

Connector Type	Feature	Model No.	C/R	Page
2.92mm Female		PE91060	B2	21
SMA Female		PE91308	C1	40
SMA Female	(P)	PE91064	D1	40
SMA Female	(P)	PE9779	E1	40
SMA Male		PE91312	D5	37
SMA Male	(P)	PE91062	E5	37
SMA Male	(P)	PE9513	A6	37
SMP Female		PE91065	E2	42
SMP Female		PE91065	E2	42
SMP In-Series:				
Female to Female		PE91102	E7	41
Female to Female		PE9776	A1	42
Female to Female		PE91068	B1	42
Female to Female		PE91072	C1	42
Female to Female		PE91099	D1	42
Female to Female		PE91101	E1	42
Female to Female		PE9775	A2	42
Female to Female		PE9777	B2	42
SMP Male To:				
2.4mm Female		PE91048	B6	19
SMA Female	(P) (PM)	PE91057	C7	39
SMA Female	(P) (PM)	PE91059	B1	40
Snap-On MMBX Jack To:				
SMA Female	(SO)	PE91363	E1	39
SMA Male	(SO)	PE91362	D1	37
Snap-On MMBX Plug To:				
Push-On SMP Female	(PO) (SO)	PE91364	D2	42
SMA Female	(SO)	PE91361	D1	39
SMA Male	(SO)	PE91360	C1	37
Snap-On QMA Female To:				
SMA Male	(SO)	PE91346	A5	33
Snap-On SMA Female	(SO)	PE91347	B5	33
Snap-On QMA Male To:				
SMA Female	(SO)	PE91345	E4	33
Snap-On SMA Male	(SO)	PE91344	D4	33
Snap-On SMA Female To:				
Snap-On QMA Female	(SO)	PE91347	B5	33
Snap-On SMA Male To:				
Snap-On QMA Male	(SO)	PE91344	D4	33
SSMA Female To:				
BNC Male		PE9191	B5	42
N Female		PE9354	D5	42
N Male		PE9352	C5	42
SMA Female		PE9399	B2	40
SMA Male		PE9063	C6	37
SSMA In-Series:				
Female to Female		PE9192	A4	42
Female to Female	(B) (PM)	PE9189	B4	42
Male to Female		PE9358	C3	42
Male to Female	(QD)	PE9685	D3	42
Male to Female	90º	PE9334	E3	42
Male to Male		PE9357	B3	42
SSMA Male To:				
2.92mm Female		PE9768	C2	21
BNC Female		PE91046	E4	42
BNC Male		PE9213	D4	42
N Male		PE9351	A5	42
SMA Female		PE9188	A2	40
SMA Male		PE9187	B6	37
SSMB Jack To:				
BNC Female		PE9394	D6	42
BNC Male		PE9392	C6	42
SMA Male		PE9401	D6	37
SSMB Plug To:				
BNC Female		PE9395	B6	42
BNC Male		PE9393	A6	42
SMA Female		PE9402	C2	40
SSMC In-Series:				
Jack to Jack	(B)	PE91432	C7	42
Plug to Jack		PE91434	B7	42
Plug to Plug		PE91436	A7	42
SSMC Jack To:				
SMA Female		PE91433	E2	40
SSMC Plug To:				
SMA Female		PE91380	D2	40
TNC Female To:				
7/16 DIN Female		PE91392	D3	44
7mm Sexless	(P)	PE9218	C3	44
BNC Female		PE9097	A4	44
BNC Male		PE9098	E3	44
C Male		PE9564	B4	44
FME Jack		PE9714	C4	44
Limited Detent SMP Male	(B)	PE91073	C5	44
MCX Jack		PE9544	E4	44
MCX Jack	(B) (PM)	PE9521	A5	44
MCX Plug		PE9545	D4	44
Mini UHF Male		PE9346	B5	44
N Female		PE9131	D1	33
N Female	(P)	PE9449	E1	33
N Female	(PM)	PE9552	A2	33
N Female	(B)	PE9482	B2	33
N Female	(P) (PM)	PE9450	C2	33
N Male		PE9090	D7	31
N Male	90º	PE9550	E7	31
N Male		PE91537	A1	32
Reverse Polarity SMA Female		PE9599	E6	40
Reverse Polarity SMA Male		PE9596	B6	40

Connector Type	Feature	Model No.	C/R	Page
SMA Female		PE9079	C3	40
SMA Female		PE9442	D3	40
SMA Female	(B) (PM)	PE9251	E3	40
SMA Female	(PM)	PE9276	A4	40
SMA Male		PE9078	B7	37
SMA Male		PE91507	C7	37
SMA Male	(PM)	PE9384	D7	37
UHF Male		PE9372	D5	44
TNC In-Series:				
Female to Female		PE91204	A4	43
Female to Female		PE91241	B4	43
Female to Female		PE9099	C4	43
Female to Female	(LP)	PE91174	D4	43
Female to Female	(P)	PE9444	E4	43
Female to Female		PE91381	A5	43
Female to Female	(B)	PE91430	B5	43
Female to Female	(B)	PE9154	C5	43
Female to Female	(B)	PE91205	D5	43
Female to Female	(B)	PE91242	E5	43
Female to Female	(B)	PE9287	A6	43
Female to Female	(PM)	PE9288	B6	43
Female to Male		PE9195	E3	43
Female to Male		PE9531	E6	43
Male to Female		PE91203	A2	43
Male to Female		PE91240	B2	43
Male to Female	(P)	PE91505	C2	43
Male to Female	(LP)	PE91173	D2	43
Male to Female		PE9270	E2	43
Male to Female	(P)	PE9443	A3	43
Male to Female	(QD)	PE9561	B3	43
Male to Female	90º	PE9100	C3	43
Male to Female		PE9290	D3	43
Male to Female		PE9532	D6	43
Male to Male	(LP)	PE91172	E7	42
Male to Male		PE91202	A1	43
Male to Male		PE91239	B1	43
Male to Male		PE9091	C1	43
Male to Male		PE9445	D1	43
Male to Male	90º	PE9560	E1	43
TNC Male To:				
7/16 DIN Female		PE9638	D7	43
7mm Sexless	(P)	PE9219	C7	43
BNC Female		PE9088	A1	44
BNC Female	90º	PE9783	B1	44
BNC Male		PE91449	E7	43
C Female		PE9562	C1	44
FME Jack		PE9713	A2	44
FME Plug		PE9699	D1	44
FME Plug	90º	PE9700	E1	44
HN Male		PE9563	B2	44
MCX Jack		PE9542	D2	44
MCX Plug		PE9543	C2	44
Mini UHF Female		PE9345	E2	44
N Female		PE9089	A1	33
N Female	(P)	PE91506	B1	33
N Female	90º	PE9263	C1	33
N Male		PE9130	B7	31
N Male	(P)	PE9446	C7	31
Reverse Polarity SMA Female		PE9598	D6	40
Reverse Polarity SMA Male		PE9597	A6	40
SMA Female		PE9077	A3	40
SMA Female		PE9440	B3	40
SMA Male		PE9076	E6	37
SMA Male		PE9439	A7	37
SMC Jack		PE9226	A3	44
UHF Female		PE9291	B3	44
UHF Female To:				
75 Ohm F Female		PE9167	A2	45
BNC Female		PE9421	E1	45
BNC Male		PE91329	D1	45
Mini UHF Male		PE91447	B2	45
N Female		PE9385	E2	33
N Male		PE9111	C1	32
SMA Male		PE9400	E7	37
TNC Male		PE9291	B3	44
UHF In-Series:				
Female to Female		PE9094	A7	44
Female to Female	(B) (PM)	PE9114	B7	44
Female to Male		PE9095	E6	44
Male to Female	90º	PE9209	D6	44
Male to Male		PE91487	C6	44
UHF Male To:				
75 Ohm F Female		PE9165	A1	45
BNC Female		PE91328	E7	44
BNC Male		PE9201	D7	44
FME Plug		PE9701	B1	45
Mini UHF Female		PE9348	C1	45
N Female		PE9112	D2	33
N Male		PE9113	B1	32
SMA Female		PE9415	B4	40
TNC Female		PE9372	D5	44
UMCX Jack To:				
SMA Female		PE91006	D4	40
SMA Male		PE91007	A1	38
UMCX Plug To:				
SMA Female		PE91005	C4	40

Feature: (B) Bulkhead Mount / (H) Hermetically Sealed / (I) Isolated Sealed / (LP) Low PIM / (P) Precision / (PM) Panel Mount / (PO) Push On / (QD) Quick Disconnect / (R) Radius Right Angle / (RU) Ruggedized / (SO) Snap-On

LOW PIM ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	**4.1/9.5 Mini DIN Between Series**	Low PIM PRICE 1-24 $65.02 25-49 $61.77 50-99 $58.52 100+ $55.92 **4.1/9.5 Mini DIN Male to N Male** VSWR 1.25:1 to 6 GHz **Model No: PE91092**	Low PIM PRICE 1-24 $63.25 25-49 $60.09 50-99 $56.93 100+ $54.40 **4.1/9.5 Mini DIN Male to N Female** VSWR 1.25:1 to 6 GHz **Model No: PE91093**	Low PIM PRICE 1-24 $65.02 25-49 $61.77 50-99 $58.52 100+ $55.92 **4.1/9.5 Mini DIN Female to N Male** VSWR 1.25:1 to 6 GHz **Model No: PE91094**	Low PIM PRICE 1-24 $65.02 25-49 $61.77 50-99 $58.52 100+ $55.92 **4.1/9.5 Mini DIN Female to N Female** VSWR 1.25:1 to 6 GHz **Model No: PE91095**
2	**4.3 Non Constant In-Series**	Low PIM PRICE 1-24 $39.02 25-49 $37.07 50-99 $35.12 100+ $33.56 **4.3-10 Male to 4.3-10 Male** VSWR 1.25:1 to 6 GHz **Model No: PE91466**	Low PIM PRICE 1-24 $88.05 25-49 $83.65 50-99 $79.25 100+ $75.72 **4.3-10 Male to 4.3-10 Male** VSWR 1.08:1 to 6 GHz **Model No: PE91385**	Low PIM PRICE 1-24 $44.10 25-49 $41.90 50-99 $39.69 100+ $37.93 **4.3-10 Male to 4.3-10 Female** VSWR 1.25:1 to 6 GHz **Model No: PE91465**	Low PIM PRICE 1-24 $88.05 25-49 $83.65 50-99 $79.25 100+ $75.72 **4.3-10 Male to 4.3-10 Female Right Angle** VSWR 1.2:1 to 3 GHz **Model No: PE91467**
3	Low PIM PRICE 1-24 $89.17 25-49 $85.60 50-99 $82.93 100+ $81.14 **4.3-10 Male to 4.3-10 Female** VSWR 1.08:1 to 6 GHz **Model No: PE91387**	Low PIM PRICE 1-24 $44.10 25-49 $41.90 50-99 $39.69 100+ $37.93 **4.3-10 Female to 4.3-10 Female** VSWR 1.25:1 to 6 GHz **Model No: PE91464**	Low PIM PRICE 1-24 $90.97 25-49 $86.42 50-99 $81.87 100+ $78.23 **4.3-10 Female to 4.3-10 Female** VSWR 1.08:1 to 6 GHz **Model No: PE91386**	**4.3 Non Constant Between Series**	Low PIM PRICE 1-24 $39.02 25-49 $37.07 50-99 $35.12 100+ $33.56 **4.3-10 Male to N Male** VSWR 1.25:1 to 6 GHz **Model No: PE91476**
4	Low PIM PRICE 1-24 $53.33 25-49 $50.66 50-99 $48.00 100+ $45.86 **QD 4.3-10 Male to N Male** VSWR 1.25:1 to 6 GHz **Model No: PE91480**	Low PIM PRICE 1-24 $39.02 25-49 $37.07 50-99 $35.12 100+ $33.56 **4.3-10 Male to N Female** VSWR 1.25:1 to 6 GHz **Model No: PE91474**	Low PIM PRICE 1-24 $39.02 25-49 $37.07 50-99 $35.12 100+ $33.56 **4.3-10 Male to N Female** VSWR 1.25:1 to 6 GHz **Model No: PE91477**	Low PIM PRICE 1-24 $51.32 25-49 $48.75 50-99 $46.19 100+ $44.14 **QD 4.3-10 Male to N Female** VSWR 1.25:1 to 6 GHz **Model No: PE91478**	Low PIM PRICE 1-24 $62.14 25-49 $59.03 50-99 $55.93 100+ $53.44 **4.3-10 Male to N Female Right Angle** VSWR 1.25:1 to 6 GHz **Model No: PE91483**
5	Low PIM PRICE 1-24 $92.71 25-49 $88.07 50-99 $83.44 100+ $79.73 **4.3-10 Male to N Female** VSWR 1.08:1 to 6 GHz **Model No: PE91389**	Low PIM PRICE 1-24 $35.29 25-49 $33.53 50-99 $31.76 100+ $30.35 **4.3-10 Male to SMA Female** VSWR 1.15:1 to 6 GHz **Model No: PE91484**	Low PIM PRICE 1-24 $45.86 25-49 $43.57 50-99 $41.27 100+ $39.44 **4.3-10 Female to N Male** VSWR 1.25:1 to 6 GHz **Model No: PE91479**	Low PIM PRICE 1-24 $43.25 25-49 $41.09 50-99 $38.93 100+ $37.20 **QD 4.3-10 Female to N Male** VSWR 1.25:1 to 6 GHz **Model No: PE91481**	Low PIM PRICE 1-24 $39.87 25-49 $37.88 50-99 $35.88 100+ $34.29 **4.3-10 Female to N Female** VSWR 1.25:1 to 6 GHz **Model No: PE91475**
6	Low PIM PRICE 1-24 $43.02 25-49 $40.87 50-99 $38.72 100+ $37.00 **QD 4.3-10 Female to N Female** VSWR 1.25:1 to 6 GHz **Model No: PE91482**	**7/16 DIN In-Series**	Low PIM PRICE 1-9 $123.52 10-24 $117.34 25-49 $111.17 50+ $106.23 **7/16 DIN Male to 7/16 DIN Male** Max. Freq. 8 GHz **Model No: PE91039**	Low PIM PRICE 1-9 $117.66 10-24 $111.78 25-49 $105.89 50+ $101.19 **7/16 DIN Male to 7/16 DIN Female** Max. Freq. 8 GHz **Model No: PE91028**	Low PIM PRICE 1-9 $117.66 10-24 $111.78 25-49 $105.89 50+ $101.19 **7/16 DIN Female to 7/16 DIN Female** Max. Freq. 8 GHz **Model No: PE91029**
7	Low PIM PRICE 1-9 $154.56 10-24 $146.83 25-49 $139.10 50+ $132.92 **7/16 DIN Female to 7/16 DIN Female Bulkhead** Max. Freq. 8 GHz **Model No: PE91038**	**7/16 DIN Between Series**	Low PIM PRICE 1-24 $85.09 25-49 $80.84 50-99 $76.58 100+ $73.18 **7/16 DIN Male to 4.1/9.5 Mini DIN Male** VSWR 1.25:1 to 6 GHz **Model No: PE91088**	Low PIM PRICE 1-24 $40.72 25-49 $38.68 50-99 $36.65 100+ $35.02 **7/16 DIN Male to 4.3-10 Male** VSWR 1.25:1 to 6 GHz **Model No: PE91468**	Low PIM PRICE 1-24 $44.10 25-49 $41.90 50-99 $39.69 100+ $37.93 **7/16 DIN Male to 4.3-10 Female** VSWR 1.25:1 to 6 GHz **Model No: PE91469**

See Our Website For Current Pricing & Real-Time Stock Availability!

LOW PIM ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 Low PIM PRICE 1-24 $76.11 25-49 $72.30 50-99 $68.50 100+ $65.45 **7/16 DIN Male to 4.3-10 Female** VSWR 1.08:1 to 6 GHz **Model No: PE91390**	 Low PIM PRICE 1-24 $85.09 25-49 $80.84 50-99 $76.58 100+ $73.18 **7/16 DIN Female to 4.1/9.5 Mini DIN Male** VSWR 1.25:1 to 6 GHz **Model No: PE91090**	 Low PIM PRICE 1-24 $85.09 25-49 $80.84 50-99 $76.58 100+ $73.18 **7/16 DIN Female to 4.1/9.5 Mini DIN Female** VSWR 1.25:1 to 6 GHz **Model No: PE91091**	 Low PIM PRICE 1-24 $43.25 25-49 $41.09 50-99 $38.93 100+ $37.20 **7/16 DIN Female to 4.3-10 Male** VSWR 1.2:1 to 6 GHz **Model No: PE91470**	 Low PIM PRICE 1-24 $59.55 25-49 $56.57 50-99 $53.60 100+ $51.21 **7/16 DIN Female to QD 4.3-10 Male** VSWR 1.2:1 to 6 GHz **Model No: PE91472**
2	 Low PIM PRICE 1-9 $121.83 10-24 $115.74 25-49 $109.65 50+ $104.77 **7/16 DIN Female to 4.3-10 Male** VSWR 1.08:1 to 6 GHz **Model No: PE91391**	 Low PIM PRICE 1-24 $44.10 25-49 $41.90 50-99 $39.69 100+ $37.93 **7/16 DIN Female to 4.3-10 Female** VSWR 1.25:1 to 6 GHz **Model No: PE91471**	 Low PIM PRICE 1-24 $44.18 25-49 $41.97 50-99 $39.76 100+ $37.99 **7/16 DIN Female to QD 4.3-10 Female** VSWR 1.2:1 to 6 GHz **Model No: PE91473**	***N In-Series***	 Low PIM PRICE 1-24 $103.84 25-49 $98.65 50-99 $93.46 100+ $89.30 **N Male to N Male** Max. Freq. 12.4 GHz **Model No: PE91034**
3	 Low PIM PRICE 1-24 $106.63 25-49 $101.30 50-99 $95.97 100+ $91.70 **N Male to N Female** Max. Freq. 12.4 GHz **Model No: PE91040**	 Low PIM PRICE 1-24 $78.39 25-49 $74.47 50-99 $70.55 100+ $67.42 **N Female to N Female** VSWR 1.2:1 to 6 GHz **Model No: PE91140**	 Low PIM PRICE 1-24 $70.22 25-49 $66.71 50-99 $63.20 100+ $60.39 **N Female to N Female Bulkhead** VSWR 1.2:1 to 6 GHz **Model No: PE91179**	***N Between Series***	 Low PIM PRICE 1-24 $81.38 25-49 $77.31 50-99 $73.24 100+ $69.99 **N Male to 4.3-10 Female** VSWR 1.08:1 to 6 GHz **Model No: PE91388**
4	 Low PIM PRICE 1-24 $93.44 25-49 $88.77 50-99 $84.10 100+ $80.36 **N Male to 7/16 DIN Male** Max. Freq. 8 GHz **Model No: PE91030**	 Low PIM PRICE 1-24 $115.11 25-49 $109.35 50-99 $103.60 100+ $98.99 **N Male to 7/16 DIN Female** Max. Freq. 8 GHz **Model No: PE91032**	 Low PIM PRICE 1-24 $52.34 25-49 $49.72 50-99 $47.11 100+ $45.01 **N Male to SMA Female** VSWR 1.2:1 to 6 GHz **Model No: PE91177**	 Low PIM PRICE 1-24 $107.77 25-49 $102.38 50-99 $96.99 100+ $92.68 **N Female to 7/16 DIN Male** Max. Freq. 8 GHz **Model No: PE91031**	 Low PIM PRICE 1-24 $100.12 25-49 $95.11 50-99 $90.11 100+ $86.10 **N Female to 7/16 DIN Female** Max. Freq. 8 GHz **Model No: PE91033**
5	 Low PIM PRICE 1-9 $153.30 10-24 $145.64 25-49 $137.97 50+ $131.84 **N Female to 7/16 DIN Female** Max. Freq. 8 GHz **Model No: PE9180**	 Low PIM PRICE 1-24 $53.30 25-49 $50.64 50-99 $47.97 100+ $45.84 **N Female to SMA Male** VSWR 1.2:1 to 6 GHz **Model No: PE91178**	***SMA Between Series***	 Low PIM PRICE 1-24 $92.67 25-49 $88.04 50-99 $83.40 100+ $79.70 **SMA Female to 7/16 DIN Male** VSWR 1.09:1 to 7.5 GHz **Model No: PE91036**	 Low PIM PRICE 1-24 $93.44 25-49 $88.77 50-99 $84.10 100+ $80.36 **SMA Female to 7/16 DIN Female** Max. Freq. 8 GHz **Model No: PE91042**
6	***TNC In-Series***	 Low PIM PRICE 1-24 $67.62 25-49 $64.24 50-99 $60.86 100+ $58.15 **TNC Male to TNC Male** VSWR 1.25:1 to 6 GHz **Model No: PE91172**	 Low PIM PRICE 1-24 $64.44 25-49 $61.22 50-99 $58.00 100+ $55.42 **TNC Male to TNC Female** VSWR 1.25:1 to 6 GHz **Model No: PE91173**	 Low PIM PRICE 1-24 $59.06 25-49 $56.11 50-99 $53.15 100+ $50.79 **TNC Female to TNC Female** VSWR 1.25:1 to 6 GHz **Model No: PE91174**	***Visit pasternack.com for our complete offering of adapters***

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	**1.0mm In-Series** →	PRICE: 1-24 $1,722.55; 25-49 $1,601.97; 50-99 $1,481.39; 100+ $1,378.04 **1.0mm Male to 1.0mm Male** VSWR 1.28:1 to 110 GHz Model No: PE91462	PRICE: 1-1 $1,789.73; 2-4 $1,718.14; 5-9 $1,646.55; 10+ $1,574.96 **1.0mm Female to 1.0mm Male** VSWR 1.28:1 to 110 GHz Model No: PE91461	PRICE: 1-1 $1,471.71; 2-4 $1,412.84; 5-9 $1,353.97; 10+ $1,295.10 **1.0mm Female to 1.0mm Female** VSWR 1.28:1 to 110 GHz Model No: PE91463	**1.0mm Between Series** →
2	PRICE: 1-4 $738.81; 5-9 $701.87; 10-24 $664.93; 25+ $635.38 **1.0mm Male to 1.85mm Male** VSWR 1.25:1 to 65 GHz Model No: PE91118	PRICE: 1-4 $493.83; 5-9 $469.14; 10-24 $444.45; 25+ $424.69 **1.0mm Male to 1.85mm Female** VSWR 1.35:1 to 65 GHz Model No: PE91108	PRICE: 1-4 $597.78; 5-9 $567.89; 10-24 $538.00; 25+ $514.09 **1.0mm Female to 1.85mm Male** VSWR 1.25:1 to 65 GHz Model No: PE91119	PRICE: 1-4 $493.83; 5-9 $469.14; 10-24 $444.45; 25+ $424.69 **1.0mm Female to 1.85mm Female** VSWR 1.35:1 to 65 GHz Model No: PE91109	**1.85mm In-Series** →
3	PRICE: 1-4 $784.38; 5-9 $745.16; 10-24 $705.94; 25+ $674.57 **1.85mm Male to 1.85mm Male** VSWR 1.35:1 to 67 GHz Model No: PE91085	PRICE: 1-4 $716.36; 5-9 $680.54; 10-24 $644.72; 25+ $616.07 **1.85mm Male to 1.85mm Male** VSWR 1.5:1 to 65 GHz Model No: PE9716	PRICE: 1-4 $719.61; 5-9 $683.63; 10-24 $647.65; 25+ $618.86 **1.85mm Male to 1.85mm Female** VSWR 1.35:1 to 67 GHz Model No: PE91086	PRICE: 1-4 $716.36; 5-9 $680.54; 10-24 $644.72; 25+ $616.07 **1.85mm Male to 1.85mm Female** VSWR 1.5:1 to 65 GHz Model No: PE9715	PRICE: 1-4 $730.39; 5-9 $693.87; 10-24 $657.35; 25+ $628.14 **1.85mm Female to 1.85mm Female** Max. Freq. 67 GHz Model No: PE91084
4	PRICE: 1-4 $604.10; 5-9 $573.90; 10-24 $543.69; 25+ $519.53 **1.85mm Female to 1.85mm Female** VSWR 1.25:1 to 67 GHz Model No: PE91115	**1.85mm Between Series** →	PRICE: 1-9 $423.77; 10-24 $402.58; 25-49 $381.39; NEW 50+ $364.44 **1.85mm Male to 2.4mm Male Right Angle** VSWR 1.4:1 to 50 GHz Model No: PE91157	PRICE: 1-9 $386.58; 10-24 $367.25; 25-49 $347.92; NEW 50+ $332.46 **1.85mm Male to 2.4mm Male Miter Right Angle** VSWR 1.35:1 to 50 GHz Model No: PE91518	PRICE: 1-9 $432.34; 10-24 $410.72; 25-49 $389.11; NEW 50+ $371.81 **1.85mm Male to 2.4mm Female Miter Right Angle** VSWR 1.35:1 to 50 GHz Model No: PE91511
5	PRICE: 1-24 $401.15; 25-49 $373.07; 50-99 $344.99; 100+ $320.92 **1.85mm Male to 2.92mm Male Right Angle** VSWR 1.3:1 to 40 GHz Model No: PE91161	PRICE: 1-9 $355.54; 10-24 $337.76; 25-49 $319.99; NEW 50+ $305.76 **1.85mm Male to 2.92mm Male Miter Right Angle** VSWR 1.25:1 to 40 GHz Model No: PE91519	PRICE: 1-9 $234.76; 10-24 $223.02; 25-49 $211.28; 50+ $201.89 **1.85mm Male to 3.5mm Female** VSWR 1.3:1 to 34 GHz Model No: PE9747	PRICE: 1-9 $233.30; 10-24 $221.64; 25-49 $209.97; 50+ $200.64 **1.85mm Male to N Male** VSWR 1.25:1 to 18 GHz Model No: PE9718	PRICE: 1-9 $237.54; 10-24 $225.66; 25-49 $213.79; 50+ $204.28 **1.85mm Male to N Female** VSWR 1.25:1 to 18 GHz Model No: PE9719
6	PRICE: 1-24 $423.77; 25-49 $402.58; 50-99 $381.39; NEW 100+ $364.44 **1.85mm Female to 2.4mm Female Miter Right Angle** VSWR 1.35:1 to 50 GHz Model No: PE91534	PRICE: 1-24 $401.14; 25-49 $373.06; 50-99 $344.98; 100+ $320.91 **1.85mm Female to 2.92mm Male Right Angle** VSWR 1.3:1 to 40 GHz Model No: PE91162	PRICE: 1-24 $360.23; 25-49 $335.01; 50-99 $309.80; NEW 100+ $288.18 **1.85mm Female to 2.92mm Male Miter Right Angle** VSWR 1.25:1 to 40 GHz Model No: PE91512	PRICE: 1-24 $289.82; 25-49 $269.53; 50-99 $249.25; NEW 100+ $231.86 **1.85mm Female to 2.92mm Female Right Angle** VSWR 1.3:1 to 40 GHz Model No: PE91163	PRICE: 1-24 $342.66; 25-49 $318.67; 50-99 $294.69; NEW 100+ $274.13 **1.85mm Female to 2.92mm Female Miter Right Angle** VSWR 1.25:1 to 40 GHz Model No: PE91513
7	PRICE: 1-9 $252.05; 10-24 $239.45; 25-49 $226.85; 50+ $216.76 **1.85mm Female to N Male** VSWR 1.25:1 to 18 GHz Model No: PE9720	PRICE: 1-9 $237.54; 10-24 $225.66; 25-49 $213.79; 50+ $204.28 **1.85mm Female to N Female** VSWR 1.25:1 to 18 GHz Model No: PE9721	**2.4mm In-Series** →	PRICE: 1-9 $228.28; 10-24 $216.87; 25-49 $205.45; 50+ $196.32 **2.4mm Male to 2.4mm Male** VSWR 1.3:1 to 50 GHz Model No: PE9451	PRICE: 1-9 $218.51; 10-24 $207.58; 25-49 $196.66; 50+ $187.92 **2.4mm Male to 2.4mm Female** VSWR 1.3:1 to 50 GHz Model No: PE9452

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 NEW PRICE 1-24 $395.98 25-49 $368.26 50-99 $340.54 100+ $316.78 **2.4mm Male to 2.4mm Female Right Angle** VSWR 1.4:1 to 50 GHz **Model No: PE91138**	 NEW PRICE 1-24 $371.81 25-49 $345.78 50-99 $319.76 100+ $297.45 **2.4mm Male to 2.4mm Female Miter Right Angle** VSWR 1.35:1 to 50 GHz **Model No: PE91498**	 PRICE 1-9 $215.40 10-24 $204.63 25-49 $193.86 50+ $185.24 **2.4mm Female to 2.4mm Female** VSWR 1.3:1 to 50 GHz **Model No: PE9453**	 PRICE 1-24 $212.57 25-49 $201.94 50-99 $191.31 100+ $182.81 **2.4mm Female to 2.4mm Female Bulkhead** VSWR 1.3:1 to 50 GHz **Model No: PE91459**	 PRICE 1-9 $446.64 10-24 $424.31 25-49 $401.98 50+ $384.11 **2.4mm Female to 2.4mm Female Bulkhead** VSWR 1.35:1 to 50 GHz **Model No: PE9640**
2	 NEW PRICE 1-24 $352.63 25-49 $327.95 50-99 $303.26 100+ $282.10 **2.4mm Female to 2.4mm Female Miter Right Angle** VSWR 1.35:1 to 50 GHz **Model No: PE91529**	***2.4mm Between Series***	 PRICE 1-4 $651.58 5-9 $619.00 10-24 $586.42 25+ $560.36 **2.4mm Male to 1.85mm Male** VSWR 1.3:1 to 50 GHz **Model No: PE9672**	 NEW PRICE 1-4 $342.67 5-9 $325.54 10-24 $308.40 25+ $294.70 **2.4mm Male to 1.85mm Male** VSWR 1.3:1 to 50 GHz **Model No: PE91540**	 PRICE 1-9 $389.03 10-24 $369.58 25-49 $350.13 50+ $334.57 **2.4mm Male to 1.85mm Female** VSWR 1.3:1 to 50 GHz **Model No: PE9674**
3	 PRICE 1-24 $425.47 25-49 $395.69 50-99 $365.90 100+ $340.38 **2.4mm Male to 2.92mm Male Miter Right Angle** VSWR 1.25:1 to 40 GHz **Model No: PE91508**	 PRICE 1-24 $327.24 25-49 $304.33 50-99 $281.43 100+ $261.79 **2.4mm Male to 2.92mm Female Miter Right Angle** VSWR 1.25:1 to 40 GHz **Model No: PE91502**	 PRICE 1-4 $760.36 5-9 $722.34 10-24 $684.32 25+ $653.91 **2.4mm Male to 7mm Sexless** VSWR 1.1:1 to 18 GHz **Model No: PE9458**	 PRICE 1-9 $319.50 10-24 $303.53 25-49 $287.55 50+ $274.77 **2.4mm Male to Full Detent Mini SMP Male** VSWR 1.25:1 to 50 GHz **Model No: PE91121**	 PRECISION PRICE 1-9 $226.49 10-24 $215.17 25-49 $203.84 50+ $194.78 **2.4mm Male to N Male** VSWR 1.15:1 to 18 GHz **Model No: PE9504**
4	 PRECISION PRICE 1-9 $254.58 10-24 $241.85 25-49 $229.12 50+ $218.94 **2.4mm Male to N Female** VSWR 1.15:1 to 18 GHz **Model No: PE9501**	 PRICE 1-4 $615.97 5-9 $585.17 10-24 $554.37 25+ $529.73 **2.4mm Female to 1.85mm Male** VSWR 1.3:1 to 50 GHz **Model No: PE9673**	 PRECISION NEW PRICE 1-4 $342.67 5-9 $325.54 10-24 $308.40 25+ $294.70 **2.4mm Female to 1.85mm Male** VSWR 1.3:1 to 50 GHz **Model No: PE91542**	 PRICE 1-4 $566.37 5-9 $538.05 10-24 $509.73 25+ $487.08 **2.4mm Female to 1.85mm Female** VSWR 1.3:1 to 50 GHz **Model No: PE9675**	 NEW PRICE 1-24 $332.91 25-49 $309.61 50-99 $286.30 100+ $266.33 **2.4mm Female to 2.92mm Male Miter Right Angle** VSWR 1.25:1 to 40 GHz **Model No: PE91526**
5	 NEW PRICE 1-24 $415.05 25-49 $386.00 50-99 $356.94 100+ $332.04 **2.4mm Female to 2.92mm Female Right Angle** VSWR 1.3:1 to 40 GHz **Model No: PE91111**	 NEW PRICE 1-24 $366.09 25-49 $340.46 50-99 $314.84 100+ $292.87 **2.4mm Female to 2.92mm Female Miter Right Angle** VSWR 1.25:1 to 40 GHz **Model No: PE91525**	 PRICE 1-9 $307.91 10-24 $292.51 25-49 $277.12 50+ $264.80 **2.4mm Female to Full Detent Mini SMP Male** VSWR 1.25:1 to 50 GHz **Model No: PE91122**	 PRICE 1-9 $289.51 10-24 $275.03 25-49 $260.56 50+ $248.98 **2.4mm Female to Mini SMP Female** VSWR 1.25:1 to 50 GHz **Model No: PE91123**	 PRECISION PRICE 1-9 $239.96 10-24 $227.96 25-49 $215.96 50+ $206.37 **2.4mm Female to N Male** VSWR 1.15:1 to 18 GHz **Model No: PE9503**
6	 PRECISION PRICE 1-9 $231.78 10-24 $220.19 25-49 $208.60 50+ $199.33 **2.4mm Female to N Female** VSWR 1.15:1 to 18 GHz **Model No: PE9502**	 PRICE 1-9 $291.84 10-24 $277.25 25-49 $262.66 50+ $250.98 **2.4mm Female to SMP Male** VSWR 1.25:1 to 40 GHz **Model No: PE91048**	 PRICE 1-9 $338.79 10-24 $321.85 25-49 $304.91 50+ $291.36 **2.4mm Female to SMP Female** VSWR 1.25:1 to 40 GHz **Model No: PE91055**	***2.4mm NMD Between Series***	 PRICE 1-9 $361.09 10-24 $343.04 25-49 $324.98 50+ $310.54 **2.4mm NMD Female to 2.4mm Female** Max. Freq. 50 GHz **Model No: PE91145**
7	 Ruggedized PRICE 1-9 $320.89 10-24 $304.85 25-49 $288.80 50+ $275.97 **2.4mm NMD Female to SMA Female** VSWR 1.2:1 to 27 GHz **Model No: PE91146**	***2.92mm In-Series***	 PRICE 1-9 $196.26 10-24 $186.45 25-49 $176.63 50+ $168.78 **2.92mm Male to 2.92mm Male** VSWR 1.25:1 to 40 GHz **Model No: PE9436**	 NEW PRICE 1-9 $308.68 10-24 $293.25 25-49 $277.81 50+ $265.46 **2.92mm Male to 2.92mm Male Miter Right Angle** VSWR 1.25:1 to 40 GHz **Model No: PE91516**	 PRICE 1-9 $202.89 10-24 $192.75 25-49 $182.60 50+ $174.49 **2.92mm Male to 2.92mm Female** VSWR 1.25:1 to 40 GHz **Model No: PE9437**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	NEW PRICE 1-9 $230.76 10-24 $219.22 25-49 $207.68 50+ $198.45 **2.92mm Male to 2.92mm Female** **Miter Right Angle** VSWR 1.25:1 to 40 GHz **Model No: PE91503**	 PRICE 1-24 $76.40 25-49 $72.58 50-99 $68.76 100+ $65.70 **2.92mm Female to 2.92mm Female** VSWR 1.25:1 to 40 GHz **Model No: PE91510**	 PRICE 1-9 $210.58 10-24 $200.05 25-49 $189.52 50+ $181.10 **2.92mm Female to 2.92mm Female** VSWR 1.25:1 to 40 GHz **Model No: PE9438**	NEW PRICE 1-9 $315.69 10-24 $299.91 25-49 $284.12 50+ $271.49 **2.92mm Female to 2.92mm Female** **Miter Right Angle** VSWR 1.25:1 to 40 GHz **Model No: PE91517**	 PRICE 1-9 $134.89 10-24 $128.15 25-49 $121.40 50+ $116.01 **2.92mm Female to 2.92mm Female** **Bulkhead-Mounting Hole B02** VSWR 1.25:1 to 40 GHz **Model No: PE9647**
2	 PRICE 1-24 $101.61 25-49 $97.55 50-99 $94.50 100+ $92.47 **2.92mm Female to 2.92mm Female** **4 Hole Flange** VSWR 1.25:1 to 40 GHz **Model No: PE91113**	 PRICE 1-9 $238.58 10-24 $226.65 25-49 $214.72 50+ $205.18 **2.92mm Female to 2.92mm Female** **4 Hole Flange** VSWR 1.35:1 to 40 GHz **Model No: PE9648**	NEW PRICE 1-24 $103.35 25-49 $99.22 50-99 $96.12 100+ $94.05 **2.92mm Female to 2.92mm Female** **4 Hole Flange** VSWR 1.25:1 to 40 GHz **Model No: PE91538**	***2.92mm Between Series***	 PRICE 1-4 $542.25 5-9 $515.14 10-24 $488.03 25+ $466.34 **2.92mm Male to 1.85mm Male** VSWR 1.25:1 to 40 GHz **Model No: PE9667**
3	 PRICE 1-4 $577.50 5-9 $548.63 10-24 $519.75 25+ $496.65 **2.92mm Male to 1.85mm Female** VSWR 1.25:1 to 40 GHz **Model No: PE9666**	 PRICE 1-9 $242.99 10-24 $230.84 25-49 $218.69 50+ $208.97 **2.92mm Male to 2.4mm Male** VSWR 1.15:1 to 40 GHz **Model No: PE91298**	 PRICE 1-9 $180.43 10-24 $171.41 25-49 $162.39 50+ $155.17 **2.92mm Male to 2.4mm Male** VSWR 1.3:1 to 40 GHz **Model No: PE9457**	 PRICE 1-9 $237.13 10-24 $225.27 25-49 $213.42 50+ $203.93 **2.92mm Male to 2.4mm Female** VSWR 1.25:1 to 40 GHz **Model No: PE91450**	 PRICE 1-9 $149.76 10-24 $142.27 25-49 $134.78 50+ $128.79 **2.92mm Male to 2.4mm Female** VSWR 1.3:1 to 40 GHz **Model No: PE9455**
4	 PRICE 1-9 $331.98 10-24 $318.70 25-49 $308.74 50+ $302.10 **2.92mm Male to 2.92mm Female** **Radius Right Angle** VSWR 1.5:1 to 40 GHz **Model No: PE91070**	 PRICE 1-24 $263.92 25-49 $245.45 50-99 $226.97 100+ $211.14 **2.92mm Male to 3.5mm Male** **Right Angle** VSWR 1.25:1 to 34.5 GHz **Model No: PE91165**	NEW PRICE 1-9 $234.28 10-24 $222.57 25-49 $210.85 50+ $201.48 **2.92mm Male to 3.5mm Male** **Miter Right Angle** VSWR 1.25:1 to 34.5 GHz **Model No: PE91522**	 PRICE 1-24 $263.92 25-49 $245.45 50-99 $226.97 100+ $211.14 **2.92mm Male to 3.5mm Female** **Right Angle** VSWR 1.25:1 to 34.5 GHz **Model No: PE91168**	NEW PRICE 1-24 $234.28 25-49 $217.88 50-99 $201.48 100+ $187.42 **2.92mm Male to 3.5mm Female** **Miter Right Angle** VSWR 1.25:1 to 34.5 GHz **Model No: PE91514**
5	 PRICE 1-9 $480.81 10-24 $461.58 25-49 $447.15 50+ $437.54 **2.92mm Male to 7mm Sexless** VSWR 1.1:1 to 18 GHz **Model No: PE9460**	 PRICE 1-9 $244.56 10-24 $234.78 25-49 $227.44 50+ $222.55 **2.92mm Male to Mini SMP Male** VSWR 1.25:1 to 40 GHz **Model No: PE91124**	 PRICE 1-9 $245.77 10-24 $235.94 25-49 $228.57 50+ $223.65 **2.92mm Male to Smooth Bore Mini SMP Male** VSWR 1.4:1 to 40 GHz **Model No: PE91125**	 PRICE 1-9 $240.95 10-24 $231.31 25-49 $224.08 50+ $219.26 **2.92mm Male to Mini SMP Female** VSWR 1.4:1 to 40 GHz **Model No: PE91126**	PRECISION PRICE 1-9 $257.44 10-24 $244.57 25-49 $231.70 50+ $221.40 **2.92mm Male to N Male** VSWR 1.15:1 to 18 GHz **Model No: PE9661**
6	PRECISION PRICE 1-9 $329.98 10-24 $313.48 25-49 $296.98 50+ $283.78 **2.92mm Male to N Female** VSWR 1.15:1 to 18 GHz **Model No: PE9662**	 PRICE 1-4 $651.39 5-9 $618.82 10-24 $586.25 25+ $560.20 **2.92mm Female to 1.85mm Male** VSWR 1.25:1 to 40 GHz **Model No: PE9665**	 PRICE 1-9 $269.57 10-24 $256.09 25-49 $242.61 50+ $231.83 **2.92mm Female to 2.4mm Male** VSWR 1.25:1 to 40 GHz **Model No: PE91451**	 PRICE 1-9 $140.61 10-24 $133.58 25-49 $126.55 50+ $120.92 **2.92mm Female to 2.4mm Male** VSWR 1.25:1 to 40 GHz **Model No: PE9454**	 PRICE 1-24 $252.55 25-49 $234.87 50-99 $217.19 100+ $202.04 **2.92mm Female to 2.4mm Female** VSWR 1.2:1 to 40 GHz **Model No: PE91499**
7	 PRICE 1-9 $164.77 10-24 $156.53 25-49 $148.29 50+ $141.70 **2.92mm Female to 2.4mm Female** VSWR 1.3:1 to 40 GHz **Model No: PE9456**	NEW PRICE 1-9 $234.28 10-24 $222.57 25-49 $210.85 50+ $201.48 **2.92mm Female to 3.5mm Male** **Miter Right Angle** VSWR 1.25:1 to 34.5 GHz **Model No: PE91520**	 PRICE 1-9 $237.83 10-24 $225.94 25-49 $214.05 50+ $204.53 **2.92mm Female to 3.5mm Female** VSWR 1.25:1 to 34 GHz **Model No: PE9660**	 PRICE 1-24 $235.63 25-49 $219.14 50-99 $202.64 100+ $188.50 **2.92mm Female to 3.5mm Female** **Right Angle** VSWR 1.25:1 to 34.5 GHz **Model No: PE91167**	NEW PRICE 1-9 $216.71 10-24 $205.87 25-49 $195.04 50+ $186.37 **2.92mm Female to 3.5mm Female** **Miter Right Angle** VSWR 1.25:1 to 34.5 GHz **Model No: PE91521**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 PRECISION PRICE 1-9 $538.51 10-24 $511.58 25-49 $484.66 50+ $463.12 **2.92mm Female to 7mm Sexless** VSWR 1.1:1 to 18 GHz **Model No: PE9461**	 PRICE 1-9 $244.56 10-24 $234.78 25-49 $227.44 50+ $222.55 **2.92mm Female to Full Detent Mini SMP Male** VSWR 1.35:1 to 40 GHz **Model No: PE91127**	 PRICE 1-9 $266.71 10-24 $256.04 25-49 $248.04 50+ $242.71 **2.92mm Female to Smooth Bore Mini SMP Male** VSWR 1.35:1 to 40 GHz **Model No: PE91128**	 PRICE 1-4 $802.50 5-9 $762.38 10-24 $722.25 25+ $690.15 **2.92mm Female to Mini SMP Female** VSWR 1.3:1 to 40 GHz **Model No: PE9782**	 PRECISION PRICE 1-9 $236.33 10-24 $224.51 25-49 $212.70 50+ $203.24 **2.92mm Female to N Male** VSWR 1.15:1 to 18 GHz **Model No: PE9663**
2	 PRECISION PRICE 1-9 $222.42 10-24 $211.30 25-49 $200.18 50+ $191.28 **2.92mm Female to N Female** VSWR 1.15:1 to 18 GHz **Model No: PE9664**	 PRICE 1-9 $216.77 10-24 $205.93 25-49 $195.09 50+ $186.42 **2.92mm Female to SMP Female** VSWR 1.25:1 to 40 GHz **Model No: PE91060**	 PRICE 1-9 $220.84 10-24 $209.80 25-49 $198.76 50+ $189.92 **2.92mm Female to SSMA Male** VSWR 1.25:1 to 40 GHz **Model No: PE9768**	***2.92mm NMD Between Series***	 PRICE 1-9 $361.09 10-24 $343.04 25-49 $324.98 50+ $310.54 **2.92mm NMD Female to 2.4mm Female** VSWR 1.35:1 to 40 GHz **Model No: PE91144**
3	***3.5mm In-Series***	 PRICE 1-9 $203.89 10-24 $193.70 25-49 $183.50 50+ $175.35 **3.5mm Male to 3.5mm Male** VSWR 1.25:1 to 34.5 GHz **Model No: PE9330**	 PRICE 1-24 $281.08 25-49 $261.40 50-99 $241.73 100+ $224.86 **3.5mm Male to 3.5mm Male Right Angle** VSWR 1.25:1 to 34.5 GHz **Model No: PE91169**	 NEW PRICE 1-9 $231.37 10-24 $219.80 25-49 $208.23 50+ $198.98 **3.5mm Male to 3.5mm Male Miter Right Angle** VSWR 1.35:1 to 34.5 GHz **Model No: PE91515**	 PRICE 1-9 $203.89 10-24 $193.70 25-49 $183.50 50+ $175.35 **3.5mm Male to 3.5mm Female** VSWR 1.25:1 to 34.5 GHz **Model No: PE9332**
4	 NEW PRICE 1-9 $216.14 10-24 $205.33 25-49 $194.53 50+ $185.88 **3.5mm Male to 3.5mm Female Miter Right Angle** VSWR 1.35:1 to 34.5 GHz **Model No: PE91523**	 PRICE 1-9 $185.98 10-24 $176.68 25-49 $167.38 50+ $159.94 **3.5mm Female to 3.5mm Female Bulkhead-Mounting Hole B06** VSWR 1.25:1 to 34.5 GHz **Model No: PE9678**	 PRICE 1-9 $248.65 10-24 $236.22 25-49 $223.79 50+ $213.84 **3.5mm Female to 3.5mm Female 4 Hole Flange-Mounting Hole A01** VSWR 1.25:1 to 34.5 GHz **Model No: PE9676**	 NEW PRICE 1 $219.65 **3.5mm Female to 3.5mm Female Miter Right Angle** VSWR 1.35:1 to 34.5 GHz **Model No: PE91528**	***3.5mm Between Series***
5	 PRICE 1-9 $241.22 10-24 $229.16 25-49 $217.10 50+ $207.45 **3.5mm Male to 1.85mm Male** VSWR 1.3:1 to 34 GHz **Model No: PE9746**	 PRICE 1-9 $254.27 10-24 $241.56 25-49 $228.84 50+ $218.67 **3.5mm Male to 1.85mm Female** VSWR 1.3:1 to 34 GHz **Model No: PE9745**	 PRICE 1-9 $293.38 10-24 $278.71 25-49 $264.04 50+ $252.31 **3.5mm Male to 2.4mm Male** VSWR 1.15:1 to 34 GHz **Model No: PE91294**	 PRICE 1-9 $233.89 10-24 $222.20 25-49 $210.50 50+ $201.15 **3.5mm Male to 2.4mm Male** VSWR 1.25:1 to 34 GHz **Model No: PE9649**	 NEW PRICE 1-24 $265.13 25-49 $246.57 50-99 $228.01 100+ $212.10 **3.5mm Male to 2.4mm Female** VSWR 1.3:1 to 34 GHz **Model No: PE91452**
6	 PRICE 1-9 $235.05 10-24 $223.30 25-49 $211.55 50+ $202.14 **3.5mm Male to 2.4mm Female** VSWR 1.25:1 to 34 GHz **Model No: PE9651**	 PRICE 1-9 $237.83 10-24 $225.94 25-49 $214.05 50+ $204.53 **3.5mm Male to 2.92mm Female** VSWR 1.25:1 to 34 GHz **Model No: PE9658**	 PRECISION PRICE 1-9 $325.70 10-24 $309.42 25-49 $293.13 50+ $280.10 **3.5mm Male to 7mm Sexless** VSWR 1.15:1 to 18 GHz **Model No: PE9326**	 PRECISION PRICE 1-9 $200.82 10-24 $190.78 25-49 $180.74 50+ $172.71 **3.5mm Male to N Male** VSWR 1.15:1 to 18 GHz **Model No: PE9322**	 PRECISION PRICE 1-9 $190.79 10-24 $181.25 25-49 $171.71 50+ $164.08 **3.5mm Male to N Female** VSWR 1.15:1 to 18 GHz **Model No: PE9324**
7	 PRICE 1-9 $231.29 10-24 $219.73 25-49 $208.16 50+ $198.91 **3.5mm Female to 1.85mm Female** VSWR 1.3:1 to 34 GHz **Model No: PE9748**	 PRICE 1-9 $238.85 10-24 $226.91 25-49 $214.97 50+ $205.41 **3.5mm Female to 2.4mm Male** VSWR 1.25:1 to 34 GHz **Model No: PE9650**	 PRICE 1-9 $289.05 10-24 $274.60 25-49 $260.15 50+ $248.58 **3.5mm Female to 2.4mm Female** VSWR 1.15:1 to 34 GHz **Model No: PE91291**	 PRICE 1-9 $210.03 10-24 $199.53 25-49 $189.03 50+ $180.63 **3.5mm Female to 2.4mm Female** VSWR 1.25:1 to 34 GHz **Model No: PE9652**	 NEW PRICE 1-9 $194.46 10-24 $184.74 25-49 $175.01 50+ $167.24 **3.5mm Female to 2.4mm Female** VSWR 1.15:1 to 34.5 GHz **Model No: PE91547**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-9 $233.89 10-24 $222.20 25-49 $210.50 50+ $201.15 **3.5mm Female to 2.92mm Male** VSWR 1.25:1 to 34.5 GHz **Model No: PE9659**	 PRECISION PRICE 1-9 $468.64 10-24 $445.21 25-49 $421.78 50+ $403.03 **3.5mm Female to 7mm Sexless** VSWR 1.15:1 to 18 GHz **Model No: PE9325**	 PRECISION NEW PRICE 1-9 $314.54 10-24 $298.81 25-49 $283.09 50+ $270.50 **3.5mm Female to 7mm Sexless** VSVR 1.15:1 to 18 GHz **Model No: PE91546**	 PRECISION PRICE 1-9 $188.68 10-24 $179.25 25-49 $169.81 50+ $162.26 **3.5mm Female to N Male** VSVR 1.15:1 to 18 GHz **Model No: PE9321**	 PRECISION PRICE 1-9 $191.06 10-24 $181.51 25-49 $171.95 50+ $164.31 **3.5mm Female to N Female** VSVR 1.15:1 to 18 GHz **Model No: PE9323**
2	***3.5mm NMD Between Series*** →	 PRICE 1-9 $361.09 10-24 $343.04 25-49 $324.98 50+ $310.54 **3.5mm NMD Female to 2.4mm Female** VSVR 1.25:1 to 33 GHz **Model No: PE91148**	 Ruggedized PRICE 1-9 $305.76 10-24 $290.47 25-49 $275.18 50+ $262.95 **3.5mm NMD Female to SMA Female** Max. Freq. 27 GHz **Model No: PE91147**	***7mm Between Series*** →	 PRECISION PRICE 1-9 $524.30 10-24 $503.33 25-49 $487.60 50+ $477.11 **7mm Sexless to BNC Male** VSVR 1.15:1 to 8 GHz **Model No: PE9221**
3	 PRECISION PRICE 1-9 $370.87 10-24 $352.33 25-49 $333.78 50+ $318.95 **7mm Sexless to BNC Female** VSVR 1.15:1 to 8 GHz **Model No: PE9220**	***4.1/9.5 Mini DIN In-Series*** →	 PRICE 1-24 $71.77 25-49 $68.18 50-99 $64.59 100+ $61.72 **4.1/9.5 Mini DIN Male to 4.1/9.5 Mini DIN Male** VSVR 1.25:1 to 6 GHz **Model No: PE91194**	 PRICE 1-24 $52.43 25-49 $49.81 50-99 $47.19 100+ $45.09 **4.1/9.5 Mini DIN Male to 4.1/9.5 Mini DIN Male** VSVR 1.3:1 to 6 GHz **Model No: PE91231**	 PRICE 1-24 $71.77 25-49 $68.18 50-99 $64.59 100+ $61.72 **4.1/9.5 Mini DIN Male to 4.1/9.5 Mini DIN Female** VSVR 1.25:1 to 6 GHz **Model No: PE91195**
4	 PRICE 1-24 $31.92 25-49 $30.32 50-99 $28.73 100+ $27.45 **4.1/9.5 Mini DIN Female to 4.1/9.5 Mini DIN Female** VSVR 1.3:1 to 6 GHz **Model No: PE91233**	 PRICE 1-24 $85.75 25-49 $81.46 50-99 $77.18 100+ $73.75 **4.1/9.5 Mini DIN Female to 4.1/9.5 Mini DIN Female Bulkhead** VSVR 1.25:1 to 6 GHz **Model No: PE91197**	 PRICE 1-24 $34.08 25-49 $32.38 50-99 $30.67 100+ $29.31 **4.1/9.5 Mini DIN Female to 4.1/9.5 Mini DIN Female Bulkhead** VSVR 1.3:1 to 6 GHz **Model No: PE91234**	***4.1/9.5 Mini DIN Between Series*** →	 PRICE 1-24 $61.65 25-49 $58.57 50-99 $55.49 100+ $53.02 **4.1/9.5 Mini DIN Male to N Male** VSVR 1.25:1 to 6 GHz **Model No: PE91216**
5	 Low PIM PRICE 1-24 $65.02 25-49 $61.77 50-99 $58.52 100+ $55.92 **4.1/9.5 Mini DIN Male to N Male** VSVR 1.25:1 to 6 GHz **Model No: PE91092**	 PRICE 1-24 $67.83 25-49 $64.44 50-99 $61.05 100+ $58.33 **4.1/9.5 Mini DIN Male to N Female** VSVR 1.25:1 to 6 GHz **Model No: PE91217**	 PRICE 1-24 $70.45 25-49 $66.93 50-99 $63.41 100+ $60.59 **4.1/9.5 Mini DIN Male to N Female** VSVR 1.3:1 to 6 GHz **Model No: PE91254**	 Low PIM PRICE 1-24 $63.25 25-49 $60.09 50-99 $56.93 100+ $54.40 **4.1/9.5 Mini DIN Male to N Female** VSVR 1.25:1 to 6 GHz **Model No: PE91093**	 PRICE 1-24 $61.65 25-49 $58.57 50-99 $55.49 100+ $53.02 **4.1/9.5 Mini DIN Female to N Male** VSVR 1.25:1 to 6 GHz **Model No: PE91219**
6	 PRICE 1-24 $76.06 25-49 $72.26 50-99 $68.45 100+ $65.41 **4.1/9.5 Mini DIN Female to N Male** VSVR 1.3:1 to 6 GHz **Model No: PE91256**	 Low PIM PRICE 1-24 $65.02 25-49 $61.77 50-99 $58.52 100+ $55.92 **4.1/9.5 Mini DIN Female to N Male** VSVR 1.25:1 to 6 GHz **Model No: PE91094**	 PRICE 1-24 $60.50 25-49 $57.48 50-99 $54.45 100+ $52.03 **4.1/9.5 Mini DIN Female to N Female** VSVR 1.25:1 to 6 GHz **Model No: PE91218**	 PRICE 1-24 $66.54 25-49 $63.21 50-99 $59.89 100+ $57.22 **4.1/9.5 Mini DIN Female to N Female** VSVR 1.3:1 to 6 GHz **Model No: PE91255**	 Low PIM PRICE 1-24 $65.02 25-49 $61.77 50-99 $58.52 100+ $55.92 **4.1/9.5 Mini DIN Female to N Female** VSVR 1.25:1 to 6 GHz **Model No: PE91095**
7	***4.3 Non Constant In-Series*** →	 Low PIM PRICE 1-24 $39.02 25-49 $37.07 50-99 $35.12 100+ $33.56 **4.3-10 Male to 4.3-10 Male** VSVR 1.25:1 to 6 GHz **Model No: PE91466**	 Low PIM PRICE 1-24 $88.05 25-49 $83.65 50-99 $79.25 100+ $75.72 **4.3-10 Male to 4.3-10 Male** VSWR 1.08:1 to 6 GHz **Model No: PE91385**	 Low PIM PRICE 1-24 $44.10 25-49 $41.90 50-99 $39.69 100+ $37.93 **4.3-10 Male to 4.3-10 Female** VSWR 1.25:1 to 6 GHz **Model No: PE91465**	 Low PIM PRICE 1-24 $88.05 25-49 $83.65 50-99 $79.25 100+ $75.72 **4.3-10 Male to 4.3-10 Female Right Angle** VSWR 1.2:1 to 3 GHz **Model No: PE91467**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	Low PIM PRICE 1-24 $89.17 25-49 $85.60 50-99 $82.93 100+ $81.14 **4.3-10 Male to 4.3-10 Female** VSWR 1.08:1 to 6 GHz **Model No: PE91387**	Low PIM PRICE 1-24 $44.10 25-49 $41.90 50-99 $39.69 100+ $37.93 **4.3-10 Female to 4.3-10 Female** VSWR 1.25:1 to 6 GHz **Model No: PE91464**	Low PIM PRICE 1-24 $90.97 25-49 $86.42 50-99 $81.87 100+ $78.23 **4.3-10 Female to 4.3-10 Female** VSWR 1.08:1 to 6 GHz **Model No: PE91386**	***4.3 Non Constant Between Series*** →	Low PIM PRICE 1-24 $39.02 25-49 $37.07 50-99 $35.12 100+ $33.56 **4.3-10 Male to N Male** VSWR 1.25:1 to 6 GHz **Model No: PE91476**
2	Low PIM PRICE 1-24 $53.33 25-49 $50.66 50-99 $48.00 100+ $45.86 **QD 4.3-10 Male to N Male** VSWR 1.25:1 to 6 GHz **Model No: PE91480**	Low PIM PRICE 1-24 $39.02 25-49 $37.07 50-99 $35.12 100+ $33.56 **4.3-10 Male to N Female** VSWR 1.25:1 to 6 GHz **Model No: PE91474**	Low PIM PRICE 1-24 $39.02 25-49 $37.07 50-99 $35.12 100+ $33.56 **4.3-10 Male to N Female** VSWR 1.25:1 to 6 GHz **Model No: PE91477**	Low PIM PRICE 1-24 $51.32 25-49 $48.75 50-99 $46.19 100+ $44.14 **QD 4.3-10 Male to N Female** VSWR 1.25:1 to 6 GHz **Model No: PE91478**	Low PIM PRICE 1-24 $62.14 25-49 $59.03 50-99 $55.93 100+ $53.44 **4.3-10 Male to N Female Right Angle** VSWR 1.25:1 to 6 GHz **Model No: PE91483**
3	Low PIM PRICE 1-24 $92.71 25-49 $88.07 50-99 $83.44 100+ $79.73 **4.3-10 Male to N Female** VSWR 1.08:1 to 6 GHz **Model No: PE91389**	Low PIM PRICE 1-24 $35.29 25-49 $33.53 50-99 $31.76 100+ $30.35 **4.3-10 Male to SMA Female** VSWR 1.15:1 to 6 GHz **Model No: PE91484**	Low PIM PRICE 1-24 $45.86 25-49 $43.57 50-99 $41.27 100+ $39.44 **4.3-10 Female to N Male** VSWR 1.25:1 to 6 GHz **Model No: PE91479**	Low PIM PRICE 1-24 $43.25 25-49 $41.09 50-99 $38.93 100+ $37.20 **QD 4.3-10 Female to N Male** VSWR 1.25:1 to 6 GHz **Model No: PE91481**	Low PIM PRICE 1-24 $39.87 25-49 $37.88 50-99 $35.88 100+ $34.29 **4.3-10 Female to N Female** VSWR 1.25:1 to 6 GHz **Model No: PE91475**
4	Low PIM PRICE 1-24 $43.02 25-49 $40.87 50-99 $38.72 100+ $37.00 **QD 4.3-10 Female to N Female** VSWR 1.25:1 to 6 GHz **Model No: PE91482**	***7/16 DIN In-Series*** →	 PRICE 1-24 $93.75 25-49 $89.06 50-99 $84.38 100+ $80.63 **7/16 DIN Male to 7/16 DIN Male** VSWR 1.15:1 to 6 GHz **Model No: PE91190**	 PRICE 1-24 $97.84 25-49 $92.95 50-99 $88.06 100+ $84.14 **7/16 DIN Male to 7/16 DIN Male** VSWR 1.25:1 to 6 GHz **Model No: PE91227**	Low PIM PRICE 1-9 $123.52 10-24 $117.34 25-49 $111.17 50+ $106.23 **7/16 DIN Male to 7/16 DIN Male** Max. Freq. 8 GHz **Model No: PE91039**
5	 PRICE 1-24 $72.12 25-49 $68.51 50-99 $64.91 100+ $62.02 **7/16 DIN Male to 7/16 DIN Female** VSWR 1.15:1 to 6 GHz **Model No: PE91191**	 PRICE 1-24 $74.37 25-49 $70.65 50-99 $66.93 100+ $63.96 **7/16 DIN Male to 7/16 DIN Female** VSWR 1.25:1 to 6 GHz **Model No: PE91228**	 PRICE 1-9 $139.42 10-24 $132.45 25-49 $125.48 50+ $119.90 **7/16 DIN Male to 7/16 DIN Female** VSWR 1.35:1 to 7.5 GHz **Model No: PE91027**	Low PIM PRICE 1-9 $117.66 10-24 $111.78 25-49 $105.89 50+ $101.19 **7/16 DIN Male to 7/16 DIN Female** Max. Freq. 8 GHz **Model No: PE91028**	 PRICE 1-24 $89.14 25-49 $84.68 50-99 $80.23 100+ $76.66 **7/16 DIN Male to 7/16 DIN Female Right Angle** VSWR 1.25:1 to 6 GHz **Model No: PE91117**
6	 PRICE 1-9 $281.43 10-24 $267.36 25-49 $253.29 50+ $242.03 **7/16 DIN Female to 7/16 DIN Male Tee** **Model No: PE9557**	 PRICE 1-24 $80.12 25-49 $76.11 50-99 $72.11 100+ $68.90 **7/16 DIN Female to 7/16 DIN Female** VSWR 1.15:1 to 6 GHz **Model No: PE91192**	 PRICE 1-24 $65.59 25-49 $62.31 50-99 $59.03 100+ $56.41 **7/16 DIN Female to 7/16 DIN Female** VSWR 1.25:1 to 6 GHz **Model No: PE91229**	Low PIM PRICE 1-9 $117.66 10-24 $111.78 25-49 $105.89 50+ $101.19 **7/16 DIN Female to 7/16 DIN Female** Max. Freq. 8 GHz **Model No: PE91029**	 PRICE 1-9 $131.23 10-24 $124.67 25-49 $118.11 50+ $112.86 **7/16 DIN Female to 7/16 DIN Female** **Model No: PE9409**
7	 PRICE 1-9 $294.61 10-24 $279.88 25-49 $265.15 50+ $253.36 **7/16 DIN Female to 7/16 DIN Female Tee** **Model No: PE9556**	Low PIM PRICE 1-9 $154.56 10-24 $146.83 25-49 $139.10 50+ $132.92 **7/16 DIN Female to 7/16 DIN Female Bulkhead** Max. Freq. 8 GHz **Model No: PE91038**	 PRICE 1-9 $280.39 10-24 $266.37 25-49 $252.35 50+ $241.14 **7/16 DIN Female to 7/16 DIN Female Bulkhead** **Model No: PE9414**	 PRICE 1-24 $108.90 25-49 $103.46 50-99 $98.01 100+ $93.65 **7/16 DIN Female to 7/16 DIN Female Bulkhead** VSWR 1.25:1 to 6 GHz **Model No: PE91193**	 PRICE 1-24 $102.50 25-49 $97.38 50-99 $92.25 100+ $88.15 **7/16 DIN Female to 7/16 DIN Female Bulkhead** VSWR 1.25:1 to 6 GHz **Model No: PE91230**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	**7/16 DIN Between Series** →	PRICE 1-24 $73.53; 25-49 $69.85; 50-99 $66.18; 100+ $63.24 **7/16 DIN Male to 4.1/9.5 Mini DIN Male** VSWR 1.25:1 to 6 GHz **Model No: PE91206**	PRICE 1-24 $42.91; 25-49 $40.76; 50-99 $38.62; 100+ $36.90 **7/16 DIN Male to 4.1/9.5 Mini DIN Male** VSWR 1.3:1 to 6 GHz **Model No: PE91243**	PRICE 1-24 $85.09; 25-49 $80.84; 50-99 $76.58; 100+ $73.18 (Low PIM) **7/16 DIN Male to 4.1/9.5 Mini DIN Male** VSWR 1.25:1 to 6 GHz **Model No: PE91088**	PRICE 1-24 $64.33; 25-49 $61.11; 50-99 $57.90; 100+ $55.32 **7/16 DIN Male to 4.1/9.5 Mini DIN Female** VSWR 1.25:1 to 6 GHz **Model No: PE91207**
2	PRICE 1-24 $39.78; 25-49 $37.79; 50-99 $35.80; 100+ $34.21 **7/16 DIN Male to 4.1/9.5 Mini DIN Female** VSWR 1.25:1 to 6 GHz **Model No: PE91244**	PRICE 1-24 $40.72; 25-49 $38.68; 50-99 $36.65; 100+ $35.02 (Low PIM) **7/16 DIN Male to 4.3-10 Male** VSWR 1.25:1 to 6 GHz **Model No: PE91468**	PRICE 1-24 $44.10; 25-49 $41.90; 50-99 $39.69; 100+ $37.93 (Low PIM) **7/16 DIN Male to 4.3-10 Female** VSWR 1.25:1 to 6 GHz **Model No: PE91469**	PRICE 1-24 $76.11; 25-49 $72.30; 50-99 $68.50; 100+ $65.45 (Low PIM) **7/16 DIN Male to 4.3-10 Female** VSWR 1.08:1 to 6 GHz **Model No: PE91390**	PRICE 1-9 $160.81; 10-24 $152.77; 25-49 $144.73; 50+ $138.30 **7/16 DIN Male to HN Female** **Model No: PE9558**
3	PRICE 1-24 $71.77; 25-49 $68.18; 50-99 $64.59; 100+ $61.72 **7/16 DIN Male to N Male** VSWR 1.15:1 to 6 GHz **Model No: PE91211**	PRICE 1-24 $89.91; 25-49 $85.41; 50-99 $80.92; 100+ $77.32 **7/16 DIN Male to N Male** VSWR 1.25:1 to 6 GHz **Model No: PE91248**	PRICE 1-24 $69.15; 25-49 $65.69; 50-99 $62.24; 100+ $59.47 **7/16 DIN Male to N Female** VSWR 1.15:1 to 6 GHz **Model No: PE91212**	PRICE 1-24 $52.66; 25-49 $50.03; 50-99 $47.39; 100+ $45.29 **7/16 DIN Male to N Female** VSWR 1.25:1 to 6 GHz **Model No: PE91249**	PRICE 1-9 $196.93; 10-24 $187.08; 25-49 $177.24; 50+ $169.36 **7/16 DIN Male to SC Female** VSWR 1.25:1 to 7.5 GHz **Model No: PE91444**
4	PRICE 1-24 $74.94; 25-49 $71.19; 50-99 $67.45; 100+ $64.45 **7/16 DIN Female to 4.1/9.5 Mini DIN Male** VSWR 1.25:1 to 6 GHz **Model No: PE91209**	PRICE 1-24 $37.39; 25-49 $35.52; 50-99 $33.65; 100+ $32.16 **7/16 DIN Female to 4.1/9.5 Mini DIN Male** VSWR 1.25:1 to 6 GHz **Model No: PE91246**	PRICE 1-24 $85.09; 25-49 $80.84; 50-99 $76.58; 100+ $73.18 (Low PIM) **7/16 DIN Female to 4.1/9.5 Mini DIN Male** VSWR 1.25:1 to 6 GHz **Model No: PE91090**	PRICE 1-24 $68.11; 25-49 $64.70; 50-99 $61.30; 100+ $58.57 **7/16 DIN Female to 4.1/9.5 Mini DIN Female** VSWR 1.25:1 to 6 GHz **Model No: PE91208**	PRICE 1-24 $36.13; 25-49 $34.32; 50-99 $32.52; 100+ $31.07 **7/16 DIN Female to 4.1/9.5 Mini DIN Female** VSWR 1.35:1 to 6 GHz **Model No: PE91245**
5	PRICE 1-24 $85.09; 25-49 $80.84; 50-99 $76.58; 100+ $73.18 (Low PIM) **7/16 DIN Female to 4.1/9.5 Mini DIN Female** VSWR 1.25:1 to 6 GHz **Model No: PE91091**	PRICE 1-24 $37.86; 25-49 $35.97; 50-99 $34.07; 100+ $32.56 **7/16 DIN Female to 4.1/9.5 Mini DIN Female Bulkhead** VSWR 1.3:1 to 6 GHz **Model No: PE91247**	PRICE 1-24 $43.25; 25-49 $41.09; 50-99 $38.93; 100+ $37.20 (Low PIM) **7/16 DIN Female to 4.3-10 Male** VSWR 1.2:1 to 6 GHz **Model No: PE91470**	PRICE 1-24 $59.55; 25-49 $56.57; 50-99 $53.60; 100+ $51.21 (Low PIM) **7/16 DIN Female to QD 4.3-10 Male** VSWR 1.2:1 to 6 GHz **Model No: PE91472**	PRICE 1-9 $121.83; 10-24 $115.74; 25-49 $109.65; 50+ $104.77 (Low PIM) **7/16 DIN Female to 4.3-10 Male** VSWR 1.08:1 to 6 GHz **Model No: PE91391**
6	PRICE 1-24 $44.10; 25-49 $41.90; 50-99 $39.69; 100+ $37.93 (Low PIM) **7/16 DIN Female to 4.3-10 Female** VSWR 1.25:1 to 6 GHz **Model No: PE91471**	PRICE 1-24 $44.18; 25-49 $41.97; 50-99 $39.76; 100+ $37.99 (Low PIM) **7/16 DIN Female to QD 4.3-10 Female** VSWR 1.2:1 to 6 GHz **Model No: PE91473**	PRICE 1-9 $175.25; 10-24 $166.49; 25-49 $157.73; 50+ $150.72 **7/16 DIN Female to HN Male** **Model No: PE9559**	PRICE 1-24 $66.45; 25-49 $63.13; 50-99 $59.81; 100+ $57.15 **7/16 DIN Female to N Male** VSWR 1.25:1 to 6 GHz **Model No: PE91214**	PRICE 1-24 $53.37; 25-49 $50.70; 50-99 $48.03; 100+ $45.90 **7/16 DIN Female to N Male** VSWR 1.25:1 to 6 GHz **Model No: PE91251**
7	PRICE 1-24 $66.45; 25-49 $63.13; 50-99 $59.81; 100+ $57.15 **7/16 DIN Female to N Female** VSWR 1.15:1 to 6 GHz **Model No: PE91213**	PRICE 1-24 $54.22; 25-49 $51.51; 50-99 $48.80; 100+ $46.63 **7/16 DIN Female to N Female** VSWR 1.25:1 to 6 GHz **Model No: PE91250**	PRICE 1-24 $92.60; 25-49 $87.97; 50-99 $83.34; 100+ $79.64 **7/16 DIN Female to N Female Bulkhead** VSWR 1.15:1 to 6 GHz **Model No: PE91215**	PRICE 1-24 $49.35; 25-49 $46.88; 50-99 $44.42; 100+ $42.44 **7/16 DIN Female to N Female Bulkhead** VSWR 1.25:1 to 6 GHz **Model No: PE91252**	**10-32 In-Series** →

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $49.94 25-49 $47.44 50-99 $44.95 100+ $42.95 **10-32 Female to 10-32 Female** Model No: PE9756	 PRICE 1-24 $72.31 25-49 $68.69 50-99 $65.08 100+ $62.19 **10-32 Female to 10-32 Female Bulkhead** Model No: PE9757	***10-32 Between Series*** →	 PRICE 1-24 $92.50 25-49 $87.88 50-99 $83.25 100+ $79.55 **10-32 Male to BNC Male** Model No: PE9751	 PRICE 1-24 $83.97 25-49 $79.77 50-99 $75.57 100+ $72.21 **10-32 Male to BNC Female** Model No: PE9753
2	 PRICE 1-24 $108.73 25-49 $103.29 50-99 $97.86 100+ $93.51 **10-32 Male to BNC Female Bulkhead** Model No: PE9755	 PRICE 1-24 $69.20 25-49 $65.74 50-99 $62.28 100+ $59.51 **10-32 Female to BNC Male** Model No: PE9750	 PRICE 1-24 $75.43 25-49 $71.66 50-99 $67.89 100+ $64.87 **10-32 Female to BNC Female** Model No: PE9752	 PRICE 1-24 $70.94 25-49 $67.39 50-99 $63.85 100+ $61.01 **10-32 Female to BNC Female Bulkhead** Model No: PE9754	***BMA In-Series*** →
3	 PRICE 1-24 $59.74 25-49 $56.75 50-99 $53.77 100+ $51.38 **Slide-On BMA Jack to Slide-On BMA Jack** VSWR 1.2:1 to 22 GHz Model No: PE91395	***BMA Between Series*** →	 PRICE 1-9 $110.97 10-24 $105.42 25-49 $99.87 50+ $95.43 **Slide-On BMA Plug to SMA Male** VSWR 1.15:1 to 18 GHz Model No: PE91396	 PRICE 1-24 $105.14 25-49 $99.88 50-99 $94.63 100+ $90.42 **Slide-On BMA Plug to SMA Male Bulkhead** VSWR 1.15:1 to 18 GHz Model No: PE91401	 PRICE 1-9 $107.96 10-24 $102.56 25-49 $97.16 50+ $92.85 **Slide-On BMA Plug to SMA Female** VSWR 1.15:1 to 18 GHz Model No: PE91398
4	 PRICE 1-9 $128.44 10-24 $122.02 25-49 $115.60 50+ $110.46 **Slide-On BMA Plug to SMA Female Bulkhead** VSWR 1.15:1 to 18 GHz Model No: PE91402	 PRICE 1-9 $132.95 10-24 $126.30 25-49 $119.66 50+ $114.34 **Slide-On BMA Jack to SMA Male** VSWR 1.25:1 to 18 GHz Model No: PE91397	 PRICE 1-9 $156.65 10-24 $148.82 25-49 $140.99 50+ $134.72 **Slide-On BMA Jack to SMA Female** VSWR 1.25:1 to 18 GHz Model No: PE91400	 PRICE 1-9 $142.63 10-24 $135.50 25-49 $128.37 50+ $122.66 **Slide-On BMA Jack to SMA Female 2 Hole Flange** VSWR 1.25:1 to 18 GHz Model No: PE91399	***BNC In-Series*** →
5	 PRICE 1-24 $23.87 25-49 $22.68 50-99 $21.48 100+ $20.53 **BNC Male to BNC Male** VSWR 1.3:1 to 1,000 MHz Model No: PE9000	 PRICE 1-24 $62.58 25-49 $59.45 50-99 $56.32 100+ $53.82 **BNC Male to BNC Male Right Angle** Max. Freq. 4 GHz Model No: PE9758	 PRICE 1-24 $38.91 25-49 $36.96 50-99 $35.02 100+ $33.46 **BNC Male to BNC Female** VSWR 1.3:1 to 4 GHz Model No: PE9269	 PRICE 1-24 $30.32 25-49 $28.80 50-99 $27.29 100+ $26.08 **BNC Male to BNC Female Right Angle** Max. Freq. 4 GHz Model No: PE9085	 PRICE 1-24 $54.69 25-49 $51.96 50-99 $49.22 100+ $47.03 **BNC Male to BNC Female Tee** VSWR 2.1:1 to 100 MHz Model No: PE9174
6	 PRICE 1-24 $55.53 25-49 $52.75 50-99 $49.98 100+ $47.76 **BNC Male to BNC Female Tee** Max. Freq. 100 MHz Model No: PE9484	 PRICE 1-24 $23.88 25-49 $22.69 50-99 $21.49 100+ $20.54 **BNC Female to BNC Male Tee** Max. Freq. 4 GHz Model No: PE9001	 PRICE 1-24 $14.16 25-49 $13.45 50-99 $12.74 100+ $12.18 **BNC Female to BNC Female** VSWR 1.3:1 to 4 GHz Model No: PE9084	 PRICE 1-24 $26.16 25-49 $24.85 50-99 $23.54 100+ $22.50 **BNC Female to BNC Female Tee** VSWR 2.1:1 to 100 MHz Model No: PE9003	 PRICE 1-24 $92.20 25-49 $87.59 50-99 $82.98 100+ $79.29 **BNC Female to BNC Female Bulkhead-Mounting Hole B06** Model No: PE9420
7	 PRICE 1-24 $29.35 25-49 $27.88 50-99 $26.42 100+ $25.24 **BNC Female to BNC Female Bulkhead** VSWR 1.5:1 to 4 GHz Model No: PE9093	 PRICE 1-24 $31.35 25-49 $29.78 50-99 $28.22 100+ $26.96 **BNC Female to BNC Female BulkheadBulkhead** VSWR 1.5:1 to 4 GHz Model No: PE9172	 PRICE 1-24 $24.25 25-49 $23.04 50-99 $21.83 100+ $20.86 **BNC Female to BNC Female 4 Hole Flange-Mounting Hole A03** VSWR 1.3:1 to 4 GHz Model No: PE9106	***Reverse Polarity BNC In-Series*** →	 PRICE 1-24 $45.04 25-49 $42.79 50-99 $40.54 100+ $38.73 **BNC Male to Rev. Pol. BNC Female** Model No: PE9530

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $61.96 25-49 $58.86 50-99 $55.76 100+ $53.29 BNC Female to Rev. Pol. BNC Male Model No: PE9529	BNC Between Series	 PRICE 1-24 $27.57 25-49 $26.19 50-99 $24.81 100+ $23.71 BNC Male to Double Banana Binding Post Jack Model No: PE9011	 PRICE 1-24 $90.43 25-49 $85.91 50-99 $81.39 100+ $77.77 BNC Male to BNC Triax Female Model No: PE91104	 PRICE 1-24 $108.46 25-49 $103.04 50-99 $97.61 100+ $93.28 BNC Male to C Male Model No: PE9536
2	 PRICE 1-24 $63.29 25-49 $60.13 50-99 $56.96 100+ $54.43 BNC Male to C Female Model No: PE9109	 PRICE 1-24 $26.92 25-49 $25.57 50-99 $24.23 100+ $23.15 BNC Male to 75 Ohm F Male Model No: PE9152	 PRICE 1-24 $33.02 25-49 $31.37 50-99 $29.72 100+ $28.40 BNC Male to 75 Ohm F Female VSWR 1.5:1 to 300 MHz Model No: PE9150	 PRICE 1-9 $121.49 10-24 $115.42 25-49 $109.34 50+ $104.48 BNC Male to MHV Female Model No: PE9406	 PRICE 1-24 $23.73 25-49 $22.54 50-99 $21.36 100+ $20.41 BNC Male to 75 Ohm Push-On RCA Jack Max. Freq. 250 MHz Model No: PE9171
3	 PRICE 1-24 $75.56 25-49 $71.78 50-99 $68.00 100+ $64.98 BNC Male to 75 Ohm SMB Plug Model No: PE9230	 PRICE 1-24 $73.73 25-49 $70.04 50-99 $66.36 100+ $63.41 BNC Male to 75 Ohm SMC Plug Model No: PE9234	 PRICE 1-24 $100.16 25-49 $95.15 50-99 $90.14 100+ $86.14 BNC Male to 75 Ohm SMC Jack Model No: PE91044	 PRICE 1-24 $44.85 25-49 $42.61 50-99 $40.37 100+ $38.57 BNC Female to C Male VSWR 1.3:1 to 4 GHz Model No: PE9087	 PRICE 1-24 $107.70 25-49 $102.32 50-99 $96.93 100+ $92.62 BNC Female to C Female Model No: PE9537
4	 PRICE 1-24 $107.47 25-49 $102.10 50-99 $96.72 100+ $92.42 BNC Female to C Female Bulkhead-Mounting Hole G01 Model No: PE9204	 PRICE 1-24 $26.17 25-49 $24.86 50-99 $23.55 100+ $22.51 BNC Female to 75 Ohm F Male VSWR 1.3:1 to 500 MHz Model No: PE9151	 PRICE 1-24 $20.79 25-49 $19.75 50-99 $18.71 100+ $17.88 BNC Female to 75 Ohm F Female Model No: PE9153	 PRICE 1-24 $21.16 25-49 $20.10 50-99 $19.04 100+ $18.20 BNC Female to 75 Ohm RCA Plug Max. Freq. 250 MHz Model No: PE9158	 PRICE 1-24 $15.40 25-49 $14.63 50-99 $13.86 100+ $13.24 BNC Female to 75 Ohm RCA Jack Max. Freq. 250 MHz Model No: PE9015
5	 PRICE 1-24 $66.06 25-49 $62.76 50-99 $59.45 100+ $56.81 BNC Female to 75 Ohm SMB Jack VSWR 1.2:1 to 4 GHz Model No: PE9231	 PRICE 1-24 $88.72 25-49 $84.28 50-99 $79.85 100+ $76.30 BNC Female to 75 Ohm SMC Plug Model No: PE9236	C In-Series	 PRICE 1-24 $124.74 25-49 $118.50 50-99 $112.27 100+ $107.28 C Male to C Male Model No: PE9300	 PRICE 1-24 $99.95 25-49 $94.95 50-99 $89.96 100+ $85.96 C Male to C Female Right Angle Model No: PE9293
6	 PRICE 1-24 $110.00 25-49 $104.50 50-99 $99.00 100+ $94.60 C Female to C Male Tee Model No: PE9207	 PRICE 1-24 $54.08 25-49 $51.38 50-99 $48.67 100+ $46.51 C Female to C Female Model No: PE9208	 PRICE 1-24 $129.35 25-49 $122.88 50-99 $116.42 100+ $111.24 C Female to C Female Tee Model No: PE9294	 PRICE 1-24 $126.83 25-49 $120.49 50-99 $114.15 100+ $109.07 C Female to C Female Bulkhead-Mounting Hole B07 Model No: PE9186	D-Sub In-Series
7	 PRICE 1-24 $55.05 25-49 $52.30 50-99 $49.55 100+ $47.34 D-Sub Plug to D-Sub Plug Model No: PE9688	 PRICE 1-24 $54.36 25-49 $51.64 50-99 $48.92 100+ $46.75 D-Sub Plug to D-Sub Receptacle Model No: PE9687	 PRICE 1-24 $77.55 25-49 $73.67 50-99 $69.80 100+ $66.69 D-Sub Receptacle to D-Sub Receptacle Model No: PE9689	FME In-Series	 PRICE 1-24 $23.32 25-49 $22.15 50-99 $20.99 100+ $20.06 FME Plug to FME Plug Model No: PE9696

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	**FME Between Series** →	PRICE 1-24 $23.32; 25-49 $22.15; 50-99 $20.99; 100+ $20.06 FME Plug to BNC Male Model No: PE9697	PRICE 1-24 $23.82; 25-49 $22.63; 50-99 $21.44; 100+ $20.49 FME Plug to BNC Male Right Angle Model No: PE9698	PRICE 1-24 $23.32; 25-49 $22.15; 50-99 $20.99; 100+ $20.06 FME Jack to BNC Male Model No: PE9711	PRICE 1-24 $18.61; 25-49 $17.68; 50-99 $16.75; 100+ $16.00 FME Jack to BNC Female Model No: PE9712
2	**GR874 In-Series** →	PRICE 1-9 $368.45; 10-24 $350.03; 25-49 $331.61; 50+ $316.87 GR874 Sexless to GR874 Sexless Right Angle Model No: PE9286	PRICE 1-9 $404.10; 10-24 $383.90; 25-49 $363.69; 50+ $347.53 GR874 Sexless to GR874 Sexless Tee Model No: PE9285	**GR874 Between Series** →	PRICE 1-9 $176.83; 10-24 $167.99; 25-49 $159.15; 50+ $152.07 GR874 Sexless to BNC Male Model No: PE9223
3	PRICE 1-9 $184.10; 10-24 $174.90; 25-49 $165.69; 50+ $158.33 GR874 Sexless to C Female Model No: PE9301	**HN In-Series** →	PRICE 1-24 $64.58; 25-49 $61.35; 50-99 $58.12; 100+ $55.54 HN Male to HN Male VSWR 1.4:1 to 3 GHz Model No: PE9210	PRICE 1-9 $169.07; 10-24 $160.62; 25-49 $152.16; 50+ $145.40 HN Male to HN Male Right Angle Model No: PE9577	PRICE 1-24 $105.81; 25-49 $100.52; 50-99 $95.23; 100+ $91.00 HN Male to HN Female Model No: PE9576
4	PRICE 1-24 $72.45; 25-49 $68.83; 50-99 $65.21; 100+ $62.31 HN Male to HN Female Right Angle VSWR 1.5:1 to 3 GHz Model No: PE9205	PRICE 1-9 $211.07; 10-24 $200.52; 25-49 $189.96; 50+ $181.52 HN Male to HN Female Tee Model No: PE9578	PRICE 1-9 $176.00; 10-24 $167.20; 25-49 $158.40; 50+ $151.36 HN Female to HN Male Tee Model No: PE9575	PRICE 1-24 $63.60; 25-49 $60.42; 50-99 $57.24; 100+ $54.70 HN Female to HN Female Model No: PE9580	PRICE 1-9 $146.66; 10-24 $139.33; 25-49 $131.99; 50+ $126.13 HN Female to HN Female Tee Model No: PE9574
5	PRICE 1-24 $81.29; 25-49 $77.23; 50-99 $73.16; 100+ $69.91 HN Female to HN Female Bulkhead-Mounting Hole G03 VSWR 1.3:1 to 2 GHz Model No: PE9193	**HN Between Series** →	PRICE 1-24 $103.37; 25-49 $98.20; 50-99 $93.03; 100+ $88.90 HN Male to BNC Male Model No: PE9567	PRICE 1-24 $69.96; 25-49 $66.46; 50-99 $62.96; 100+ $60.17 HN Male to BNC Female VSWR 1.5:1 to 4 GHz Model No: PE9126	PRICE 1-24 $111.20; 25-49 $105.64; 50-99 $100.08; 100+ $95.63 HN Male to C Male Max. Freq. 4 GHz Model No: PE9579
6	PRICE 1-24 $88.24; 25-49 $83.83; 50-99 $79.42; 100+ $75.89 HN Male to C Female Model No: PE9296	PRICE 1-9 $229.40; 10-24 $217.93; 25-49 $206.46; 50+ $197.28 HN Male to GR874 Sexless Model No: PE9386	PRICE 1-9 $155.90; 10-24 $148.11; 25-49 $140.31; 50+ $134.07 HN Male to MHV Female Model No: PE9264	PRICE 1-24 $73.94; 25-49 $70.24; 50-99 $66.55; 100+ $63.59 HN Female to BNC Male Model No: PE9129	PRICE 1-24 $133.36; 25-49 $126.69; 50-99 $120.02; 100+ $114.69 HN Female to C Male Model No: PE9212
7	PRICE 1-9 $217.52; 10-24 $206.64; 25-49 $195.77; 50+ $187.07 HN Female to GR874 Sexless Model No: PE9387	**LC In-Series** →	PRICE 1-9 $327.03; 10-24 $310.68; 25-49 $294.33; 50+ $281.25 LC Male to LC Male Model No: PE9569	PRICE 1-9 $434.63; 10-24 $412.90; 25-49 $391.17; 50+ $373.78 LC Male to LC Female Right Angle Model No: PE9398	PRICE 1-9 $271.35; 10-24 $257.78; 25-49 $244.22; 50+ $233.36 LC Female to LC Female Model No: PE9419

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	**LC Between Series** →	PRICE: 1-9 $329.95; 10-24 $313.45; 25-49 $296.96; 50+ $283.76 LC Male to HN Female Model No: PE9181	PRICE: 1-9 $304.16; 10-24 $288.95; 25-49 $273.74; 50+ $261.58 LC Female to HN Male Model No: PE9413	**MCX In-Series** →	PRICE: 1-24 $78.35; 25-49 $74.43; 50-99 $70.52; 100+ $67.38 MCX Plug to MCX Jack VSWR 1.35:1 to 6 GHz Model No: PE9479
2	PRICE: 1-24 $24.24; 25-49 $23.03; 50-99 $21.82; 100+ $20.85 MCX Jack to MCX Jack Model No: PE9524	PRICE: 1-24 $30.30; 25-49 $28.79; 50-99 $27.27; 100+ $26.06 MCX Jack to MCX Jack Bulkhead VSWR 1.35:1 to 3 GHz Model No: PE9474	**MCX Between Series** →	PRICE: 1-24 $106.64; 25-49 $101.31; 50-99 $95.98; 100+ $91.71 MCX Plug to BNC Male Model No: PE9469	PRICE: 1-24 $90.04; 25-49 $85.54; 50-99 $81.04; 100+ $77.43 MCX Plug to BNC Female Model No: PE9467
3	PRICE: 1-24 $83.77; 25-49 $79.58; 50-99 $75.39; 100+ $72.04 MCX Jack to BNC Male Model No: PE9468	PRICE: 1-24 $107.37; 25-49 $102.00; 50-99 $96.63; 100+ $92.34 MCX Jack to BNC Female Model No: PE9466	PRICE: 1-24 $107.64; 25-49 $102.26; 50-99 $96.88; 100+ $92.57 MCX Jack to BNC Female Bulkhead-Mounting Hole B04 Model No: PE9520	**MHV In-Series** →	PRICE: 1-24 $49.33; 25-49 $46.86; 50-99 $44.40; 100+ $42.42 MHV Male to BNC Female VSWR 1.3:1 to 300 MHz Model No: PE9297
4	PRICE: 1-24 $65.74; 25-49 $62.45; 50-99 $59.17; 100+ $56.54 MHV Male to MHV Female Right Angle Max. Freq. 50 MHz Model No: PE9266	PRICE: 1-24 $77.63; 25-49 $73.75; 50-99 $69.87; 100+ $66.76 MHV Female to MHV Male Tee Max. Freq. 50 MHz Model No: PE9211	PRICE: 1-24 $41.53; 25-49 $39.45; 50-99 $37.38; 100+ $35.72 MHV Female to MHV Female VSWR 1.3:1 to 300 MHz Model No: PE9267	PRICE: 1-24 $71.38; 25-49 $67.81; 50-99 $64.24; 100+ $61.39 MHV Female to MHV Female Bulkhead Model No: PE9268	**MHV Between Series** →
5	PRICE: 1-24 $112.19; 25-49 $106.58; 50-99 $100.97; 100+ $96.48 MHV Male to SHV Plug Model No: PE9340	PRICE: 1-9 $144.33; 10-24 $137.11; 25-49 $129.90; 50+ $124.12 MHV Male to SHV Jack Model No: PE9335	PRICE: 1-9 $123.90; 10-24 $117.71; 25-49 $111.51; 50+ $106.55 MHV Female to SHV Plug Model No: PE9265	PRICE: 1-24 $74.41; 25-49 $70.69; 50-99 $66.97; 100+ $63.99 MHV Female to SHV Jack Model No: PE9339	**Mini SMP In-Series** →
6	PRICE: 1-24 $55.26; 25-49 $52.50; 50-99 $49.73; 100+ $47.52 Mini SMP Female to Mini SMP Female Max. Freq. 65 GHz Model No: PE9780	PRICE: 1-24 $31.57; 25-49 $29.99; 50-99 $28.41; 100+ $27.15 Mini SMP Female to Mini SMP Female VSWR 1.2:1 to 26.5 GHz Model No: PE91069	**Mini UHF In-Series** →	PRICE: 1-24 $18.93; 25-49 $17.98; 50-99 $17.04; 100+ $16.28 Mini UHF Male to Mini UHF Female Right Angle Model No: PE9347	PRICE: 1-24 $11.35; 25-49 $10.78; 50-99 $10.22; 100+ $9.76 Mini UHF Female to Mini UHF Male Tee Model No: PE9065
7	PRICE: 1-24 $21.20; 25-49 $20.14; 50-99 $19.08; 100+ $18.23 Mini UHF Female to Mini UHF Female Model No: PE9343	PRICE: 1-24 $19.44; 25-49 $18.47; 50-99 $17.50; 100+ $16.72 Mini UHF Female to Mini UHF Female Tee Model No: PE9066	**Mini UHF Between Series** →	PRICE: 1-24 $20.20; 25-49 $19.19; 50-99 $18.18; 100+ $17.37 Mini UHF Male to BNC Female Model No: PE9342	PRICE: 1-24 $19.40; 25-49 $18.43; 50-99 $17.46; 100+ $16.68 Mini UHF Male to FME Plug Model No: PE9705

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $18.53 25-49 $17.60 50-99 $16.68 100+ $15.94 **Mini UHF Male to FME Plug Right Angle** Model No: PE9706	 PRICE 1-24 $16.18 25-49 $15.37 50-99 $14.56 100+ $13.91 **Mini UHF Male to FME Jack** Model No: PE9709	 PRICE 1-24 $21.90 25-49 $20.81 50-99 $19.71 100+ $18.83 **Mini UHF Female to BNC Male** Model No: PE9341	 PRICE 1-24 $17.14 25-49 $16.28 50-99 $15.43 100+ $14.74 **Mini UHF Female to FME Jack** Model No: PE9710	***MMCX In-Series*** →
2	 PRICE 1-24 $100.59 25-49 $95.56 50-99 $90.53 100+ $86.51 **MMCX Plug to MMCX Jack** Model No: PE9480	 PRICE 1-24 $80.36 25-49 $76.34 50-99 $72.32 100+ $69.11 **MMCX Jack to MMCX Jack** Model No: PE9523	 PRICE 1-24 $72.00 25-49 $68.40 50-99 $64.80 100+ $61.92 **MMCX Jack to MMCX Jack Bulkhead-Mounting Hole B01** Model No: PE9522	***MMCX Between Series*** →	 PRICE 1-9 $121.30 10-24 $115.24 25-49 $109.17 50+ $104.32 **MMCX Plug to BNC Male** Model No: PE9517
3	 PRICE 1-24 $106.13 25-49 $100.82 50-99 $95.52 100+ $91.27 **MMCX Plug to MCX Plug** Model No: PE9527	 PRICE 1-24 $125.73 25-49 $119.44 50-99 $113.16 100+ $108.13 **MMCX Plug to MCX Jack** Model No: PE9525	 PRICE 1-24 $98.43 25-49 $93.51 50-99 $88.59 100+ $84.65 **MMCX Jack to BNC Male** Model No: PE9518	 PRICE 1-24 $104.47 25-49 $99.25 50-99 $94.02 100+ $89.84 **MMCX Jack to BNC Female** Model No: PE9516	 PRICE 1-24 $125.08 25-49 $118.83 50-99 $112.57 100+ $107.57 **MMCX Jack to MCX Plug** Model No: PE9528
4	 PRICE 1-24 $115.37 25-49 $109.60 50-99 $103.83 100+ $99.22 **MMCX Jack to MCX Jack** Model No: PE9526	***MMBX In-Series*** →	 PRICE 1-24 $9.87 25-49 $9.38 50-99 $8.88 100+ $8.49 **Slide-On MMBX Plug to Snap-On MMBX Plug** VSWR 1.08:1 to 12.4 GHz Model No: PE91370	 PRICE 1-24 $14.80 25-49 $14.06 50-99 $13.32 100+ $12.73 **Slide-On MMBX Plug to Slide-On MMBX Plug** VSWR 1.15:1 to 12.4 GHz Model No: PE91371	 PRICE 1-24 $18.80 25-49 $17.86 50-99 $16.92 100+ $16.17 **Snap-On MMBX Plug to Slide-On MMBX Plug** VSWR 1.25:1 to 12.4 GHz Model No: PE91372
5	 PRICE 1-24 $13.65 25-49 $12.97 50-99 $12.29 100+ $11.74 **Slide-On MMBX Plug to Snap-On MMBX Plug** VSWR 1.08:1 to 12.4 GHz Model No: PE91373	***N In-Series*** →	 PRICE 1-24 $64.05 25-49 $60.85 50-99 $57.65 100+ $55.08 **N Male to N Male** VSWR 1.2:1 to 6 GHz Model No: PE91198	 PRICE 1-24 $48.08 25-49 $45.68 50-99 $43.27 100+ $41.35 **N Male to N Male** VSWR 1.3:1 to 6 GHz Model No: PE91235	 PRICE 1-24 $22.50 25-49 $21.38 50-99 $20.25 100+ $19.35 **N Male to N Male** VSWR 1.3:1 to 6 GHz Model No: PE9007
6	 PRICE 1-24 $103.84 25-49 $98.65 50-99 $93.46 Low PIM 100+ $89.30 **N Male to N Male** Max. Freq. 12.4 GHz Model No: PE91034	 PRICE 1-24 $91.66 25-49 $87.08 50-99 $82.49 PRECISION NEW 100+ $78.83 **N Male to N Male** VSWR 1.15:1 to 18 GHz Model No: PE91532	 PRICE 1-24 $44.34 25-49 $42.12 50-99 $39.91 100+ $38.13 **N Male to N Male Right Angle** VSWR 1.5:1 to 11 GHz Model No: PE9198	 PRICE 1-24 $104.20 25-49 $98.99 50-99 $93.78 100+ $89.61 **N Male to N Male Tee** Model No: PE9390	 PRICE 1-24 $64.05 25-49 $60.85 50-99 $57.65 100+ $55.08 **N Male to N Female** VSWR 1.2:1 to 6 GHz Model No: PE91199
7	 PRICE 1-24 $46.37 25-49 $44.05 50-99 $41.73 100+ $39.88 **N Male to N Female** VSWR 1.3:1 to 6 GHz Model No: PE91236	 PRICE 1-24 $106.63 25-49 $101.30 50-99 $95.97 Low PIM 100+ $91.70 **N Male to N Female** Max. Freq. 12.4 GHz Model No: PE91040	 PRICE 1-24 $39.04 25-49 $37.09 50-99 $35.14 100+ $33.57 **Push-On N Male to N Female** VSWR 1.22:1 to 18 GHz Model No: PE91114	 PRICE 1-9 $90.18 10-24 $85.67 25-49 $81.16 PRECISION NEW 50+ $77.55 **N Male to N Female** VSWR 1.15:1 to 18 GHz Model No: PE91531	 PRICE 1-24 $33.58 25-49 $31.90 50-99 $30.22 100+ $28.88 **N Male to N Female** VSWR 1.3:1 to 11 GHz Model No: PE9311

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $60.84 25-49 $57.80 50-99 $54.76 100+ $52.32 **N Male to 75 Ohm N Female** **Model No: PE9349**	 PRICE 1-9 $194.68 10-24 $184.95 25-49 $175.21 50+ $167.42 **QD N Male to N Female** **Model No: PE9547**	 PRICE 1-9 $316.24 10-24 $303.59 25-49 $294.10 PRECISION 50+ $287.78 **N Male to N Female Radius Right Angle** VSWR 1.25:1 to 18 GHz **Model No: PE91350**	 PRICE 1-24 $24.79 25-49 $23.55 50-99 $22.31 100+ $21.32 **N Male to N Female Right Angle** VSWR 1.3:1 to 11 GHz **Model No: PE9086**	 PRICE 1-24 $106.88 25-49 $101.54 50-99 $96.19 100+ $91.92 **N Male to N Female Tee** **Model No: PE9481**
2	 PRICE 1-24 $44.95 25-49 $42.70 50-99 $40.46 100+ $38.66 **N Male to N Female Bulkhead** VSWR 1.3:1 to 11 GHz **Model No: PE9595**	 PRICE 1-24 $52.64 25-49 $50.01 50-99 $47.38 100+ $45.27 **N Female to 75 Ohm N Male** Max. Freq. 500 MHz **Model No: PE9350**	 PRICE 1-24 $58.63 25-49 $55.70 50-99 $52.77 100+ $50.42 **N Female to N Male Tee** Max. Freq. 11 GHz **Model No: PE9102**	 PRICE 1-24 $73.90 25-49 $70.21 50-99 $66.51 100+ $63.55 **N Female to N Female** VSWR 1.2:1 to 6 GHz **Model No: PE91200**	 PRICE 1-24 $41.65 25-49 $39.57 50-99 $37.49 100+ $35.82 **N Female to N Female** VSWR 1.3:1 to 6 GHz **Model No: PE91237**
3	 PRICE 1-24 $20.00 25-49 $19.00 50-99 $18.00 100+ $17.20 **N Female to N Female** VSWR 1.3:1 to 11 GHz **Model No: PE9006**	 PRICE 1-24 $78.39 25-49 $74.47 50-99 $70.55 Low PIM 100+ $67.42 **N Female to N Female** VSWR 1.2:1 to 6 GHz **Model No: PE91140**	 PRICE 1-24 $52.88 25-49 $50.24 50-99 $47.59 100+ $45.48 **N Female to N Female** VSWR 1.2:1 to 18 GHz **Model No: PE91141**	 PRICE 1-9 $112.93 10-24 $107.28 25-49 $101.64 PRECISION NEW 50+ $97.12 **N Female to N Female** VSWR 1.15:1 to 18 GHz **Model No: PE91530**	 PRICE 1-24 $58.69 25-49 $55.76 50-99 $52.82 100+ $50.47 **N Female to N Female Right Angle** **Model No: PE9359**
4	 PRICE 1-24 $39.44 25-49 $37.47 50-99 $35.50 100+ $33.92 **N Female to N Female Tee** VSWR 2:1 to 100 MHz **Model No: PE9101**	 PRICE 1-24 $108.90 25-49 $103.46 50-99 $98.01 100+ $93.65 **N Female to N Female Cross** **Model No: PE9548**	 PRICE 1-24 $31.98 25-49 $30.38 50-99 $28.78 100+ $27.50 **N Female to N Female Bulkhead** VSWR 1.4:1 to 3 GHz **Model No: PE9128**	 PRICE 1-24 $81.11 25-49 $77.05 50-99 $73.00 100+ $69.75 **N Female to N Female Bulkhead** Max. Freq. 11 GHz **Model No: PE9383**	 PRICE 1-24 $86.83 25-49 $82.49 50-99 $78.15 100+ $74.67 **N Female to N Female Right Angle Bulkhead-Mounting Hole G01** Max. Freq. 6 GHz **Model No: PE9541**
5	 PRICE 1-24 $35.39 25-49 $33.62 50-99 $31.85 100+ $30.44 **N Female to N Female 4 Hole Flange-Mounting Hole A05** VSWR 1.5:1 to 11 GHz **Model No: PE9173**	 PRICE 1-9 $149.73 10-24 $142.24 25-49 $134.76 PRECISION 50+ $128.77 **N Female to N Female 4 Hole Flange-Mounting Hole A05** VSWR 1.15:1 to 18 GHz **Model No: PE9429**	 PRICE 1-24 $78.62 25-49 $74.69 50-99 $70.76 100+ $67.61 **N Female to N Female Bulkhead** VSWR 1.2:1 to 6 GHz **Model No: PE91201**	 PRICE 1-24 $39.89 25-49 $37.90 50-99 $35.90 100+ $34.31 **N Female to N Female Bulkhead** VSWR 1.3:1 to 6 GHz **Model No: PE91238**	 PRICE 1-24 $70.22 25-49 $66.71 50-99 $63.20 Low PIM 100+ $60.39 **N Female to N Female Bulkhead** VSWR 1.2:1 to 6 GHz **Model No: PE91179**
6	 PRICE 1-9 $182.28 10-24 $173.17 25-49 $164.05 PRECISION 50+ $156.76 **N Female to N Female Bulkhead** VSWR 1.15:1 to 18 GHz **Model No: PE9500**	 PRICE 1-24 $54.27 25-49 $51.56 50-99 $48.84 100+ $46.67 **N Female to N Female Bulkhead** VSWR 1.5:1 to 11 GHz **Model No: PE9382**	***Reverse Polarity N In-Series*** →	 PRICE 1-24 $47.74 25-49 $45.35 50-99 $42.97 100+ $41.06 **N Male to Rev. Pol. N Female** Max. Freq. 11 GHz **Model No: PE9771**	 PRICE 1-24 $46.13 25-49 $43.82 50-99 $41.52 100+ $39.67 **N Female to Rev. Pol. N Male** Max. Freq. 11 GHz **Model No: PE9770**
7	 PRICE 1-24 $47.74 25-49 $45.35 50-99 $42.97 100+ $41.06 **Rev. Pol. N Female to Rev. Pol. N Female** VSWR 1.3:1 to 11 GHz **Model No: PE9773**	***N Between Series*** →	 PRICE 1-9 $340.94 10-24 $323.89 25-49 $306.85 PRECISION 50+ $293.21 **N Male to 7mm Sexless** VSWR 1.12:1 to 18 GHz **Model No: PE9217**	 PRICE 1-24 $81.38 25-49 $77.31 50-99 $73.24 Low PIM 100+ $69.99 **N Male to 4.3-10 Female** VSWR 1.08:1 to 6 GHz **Model No: PE91388**	 PRICE 1-24 $93.44 25-49 $88.77 50-99 $84.10 Low PIM 100+ $80.36 **N Male to 7/16 DIN Male** Max. Freq. 8 GHz **Model No: PE91030**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-9 $209.41 10-24 $198.94 25-49 $188.47 50+ $180.09 **N Male to 7/16 DIN Male** **Model No: PE9535**	 Low PIM PRICE 1-24 $115.11 25-49 $109.35 50-99 $103.60 100+ $98.99 **N Male to 7/16 DIN Female** Max. Freq. 8 GHz **Model No: PE91032**	 PRICE 1-24 $95.98 25-49 $91.18 50-99 $86.38 100+ $82.54 **N Male to 7/16 DIN Female** VSWR 1.15:1 to 6 GHz **Model No: PE91134**	 PRICE 1-24 $49.46 25-49 $46.99 50-99 $44.51 100+ $42.54 **N Male to BNC Male** VSWR 1.3:1 to 4 GHz **Model No: PE9127**	 PRECISION PRICE 1-9 $192.88 10-24 $183.24 25-49 $173.59 50+ $165.88 **N Male to BNC Male** VSWR 1.2:1 to 8 GHz **Model No: PE9489**
2	 PRICE 1-24 $112.51 25-49 $106.88 50-99 $101.26 100+ $96.76 **N Male to BNC Male Right Angle** **Model No: PE9565**	 PRICE 1-24 $23.25 25-49 $22.09 50-99 $20.93 100+ $20.00 **N Male to BNC Female** VSWR 1.3:1 to 2 GHz **Model No: PE9002**	 PRECISION PRICE 1-9 $151.49 10-24 $143.92 25-49 $136.34 50+ $130.28 **N Male to BNC Female** VSWR 1.2:1 to 8 GHz **Model No: PE9491**	 PRICE 1-24 $91.48 25-49 $86.91 50-99 $82.33 100+ $78.67 **N Male to BNC Female Right Angle** VSWR 1.2:1 to 4 GHz **Model No: PE9278**	 PRICE 1-24 $69.19 25-49 $65.73 50-99 $62.27 100+ $59.50 **N Male to BNC Female 4 Hole Flange** Max. Freq. 4 GHz **Model No: PE9388**
3	 PRICE 1-24 $108.46 25-49 $103.04 50-99 $97.61 100+ $93.28 **N Male to C Male** **Model No: PE9538**	 PRICE 1-24 $62.73 25-49 $59.59 50-99 $56.46 100+ $53.95 **N Male to C Female** Max. Freq. 11 GHz **Model No: PE91446**	 PRICE 1-24 $113.52 25-49 $107.84 50-99 $102.17 100+ $97.63 **N Male to C Female Right Angle** Max. Freq. 4 GHz **Model No: PE9239**	 PRICE 1-24 $36.20 25-49 $34.39 50-99 $32.58 100+ $31.13 **N Male to 75 Ohm F Female** VSWR 1.3:1 to 250 MHz **Model No: PE9155**	 PRICE 1-24 $26.96 25-49 $25.61 50-99 $24.26 100+ $23.19 **N Male to FME Plug** **Model No: PE9704**
4	 PRICE 1-9 $197.50 10-24 $187.63 25-49 $177.75 50+ $169.85 **N Male to GR874 Sexless** **Model No: PE9257**	 PRICE 1-24 $89.19 25-49 $84.73 50-99 $80.27 100+ $76.70 **N Male to HN Male** **Model No: PE9554**	 PRICE 1-24 $57.19 25-49 $54.33 50-99 $51.47 100+ $49.18 **N Male to HN Female** VSWR 1.3:1 to 4 GHz **Model No: PE9125**	 PRICE 1-9 $209.10 10-24 $198.65 25-49 $188.19 50+ $179.83 **N Male to LC Female** **Model No: PE9299**	 PRICE 1-24 $96.60 25-49 $92.74 50-99 $89.84 100+ $87.91 **N Male to MCX Plug** **Model No: PE9465**
5	 PRICE 1-9 $138.58 10-24 $131.65 25-49 $124.72 50+ $119.18 **N Male to MCX Jack** Max. Freq. 6 GHz **Model No: PE9464**	 PRICE 1-24 $27.36 25-49 $25.99 50-99 $24.62 100+ $23.53 **N Male to Mini UHF Female** Max. Freq. 2.5 GHz **Model No: PE9064**	 PRICE 1-9 $228.67 10-24 $217.24 25-49 $205.80 50+ $196.66 **N Male to QMA Female** Max. Freq. 11 GHz **Model No: PE9787**	 PRICE 1-9 $131.70 10-24 $125.12 25-49 $118.53 50+ $113.26 **N Male to SC Male** VSWR 1.25:1 to 11 GHz **Model No: PE9570**	 PRICE 1-9 $117.52 10-24 $111.64 25-49 $105.77 50+ $101.07 **N Male to SC Female** VSWR 1.25:1 to 11 GHz **Model No: PE9196**
6	 Low PIM PRICE 1-24 $52.34 25-49 $49.72 50-99 $47.11 100+ $45.01 **N Male to SMA Female** VSWR 1.2:1 to 6 GHz **Model No: PE91177**	 PRECISION NEW PRICE 1-24 $49.80 25-49 $47.31 50-99 $44.82 100+ $42.83 **N Male to SMA Female** VSWR 1.25:1 to 18 GHz **Model No: PE91339**	 PRICE 1-24 $106.72 25-49 $101.38 50-99 $96.05 100+ $91.78 **N Male to SMB Plug** **Model No: PE9314**	 PRICE 1-24 $71.13 25-49 $67.57 50-99 $64.02 100+ $61.17 **N Male to SMB Jack** **Model No: PE9313**	 PRICE 1-24 $105.02 25-49 $99.77 50-99 $94.52 100+ $90.32 **N Male to SMC Plug** **Model No: PE9318**
7	 PRICE 1-24 $92.84 25-49 $88.20 50-99 $83.56 100+ $79.84 **N Male to SMC Jack** **Model No: PE9317**	 PRICE 1-24 $27.58 25-49 $26.20 50-99 $24.82 100+ $23.72 **N Male to TNC Male** VSWR 1.5:1 to 11 GHz **Model No: PE9130**	 PRECISION PRICE 1-9 $169.77 10-24 $161.28 25-49 $152.79 50+ $146.00 **N Male to TNC Male** VSWR 1.15:1 to 18 GHz **Model No: PE9446**	 PRICE 1-24 $25.69 25-49 $24.41 50-99 $23.12 100+ $22.09 **N Male to TNC Female** VSWR 1.5:1 to 1,000 MHz **Model No: PE9090**	 PRICE 1-24 $91.77 25-49 $87.18 50-99 $82.59 100+ $78.92 **N Male to TNC Female Right Angle** VSWR 1.33:1 to 6 GHz **Model No: PE9550**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	NEW PRICE 1-9 $114.76 10-24 $109.02 25-49 $103.28 50+ $98.69 **N Male to TNC Female** VSWR 1.15:1 to 18 GHz **Model No: PE91537**	 PRICE 1-24 $39.10 25-49 $37.15 50-99 $35.19 100+ $33.63 **N Male to UHF Male** **Model No: PE9113**	 PRICE 1-24 $37.33 25-49 $35.46 50-99 $33.60 100+ $32.10 **N Male to UHF Female** VSWR 1.3:1 to 300 MHz **Model No: PE9111**	PRECISION PRICE 1-9 $346.32 10-24 $332.47 25-49 $322.08 50+ $315.15 **N Female to 7mm Sexless** VSWR 1.15:1 to 18 GHz **Model No: PE9216**	Low PIM PRICE 1-24 $107.77 25-49 $102.38 50-99 $96.99 100+ $92.68 **N Female to 7/16 DIN Male** Max. Freq. 8 GHz **Model No: PE91031**
2	Low PIM PRICE 1-24 $100.12 25-49 $95.11 50-99 $90.11 100+ $86.10 **N Female to 7/16 DIN Female** Max. Freq. 8 GHz **Model No: PE91033**	Low PIM PRICE 1-9 $153.30 10-24 $145.64 25-49 $137.97 50+ $131.84 **N Female to 7/16 DIN Female** Max. Freq. 8 GHz **Model No: PE9180**	 PRICE 1-24 $24.88 25-49 $23.64 50-99 $22.39 100+ $21.40 **N Female to BNC Male** VSWR 1.3:1 to 4 GHz **Model No: PE9005**	PRECISION PRICE 1-9 $150.35 10-24 $142.83 25-49 $135.32 50+ $129.30 **N Female to BNC Male** VSWR 1.2:1 to 8 GHz **Model No: PE9490**	 PRICE 1-24 $68.21 25-49 $64.80 50-99 $61.39 100+ $58.66 **N Female to BNC Male Right Angle** Max. Freq. 4 GHz **Model No: PE9566**
3	 PRICE 1-24 $89.80 25-49 $85.31 50-99 $80.82 100+ $77.23 **N Female to BNC Male 4 Hole Flange-Mounting Hole A05** **Model No: PE9123**	 PRICE 1-24 $26.36 25-49 $25.04 50-99 $23.72 100+ $22.67 **N Female to BNC Female** VSWR 1.5:1 to 3 GHz **Model No: PE9206**	PRECISION PRICE 1-9 $94.39 10-24 $89.67 25-49 $84.95 50+ $81.18 **N Female to BNC Female** VSWR 1.2:1 to 8 GHz **Model No: PE9492**	 PRICE 1-24 $71.59 25-49 $68.01 50-99 $64.43 100+ $61.57 **N Female to BNC Female Bulkhead-Mounting Hole G01** **Model No: PE9261**	 PRICE 1-24 $63.24 25-49 $60.08 50-99 $56.92 100+ $54.39 **N Female to BNC Female 4 Hole Flange-Mounting Hole A05** VSWR 1.2:1 to 6 GHz **Model No: PE9238**
4	 PRICE 1-24 $70.64 25-49 $67.11 50-99 $63.58 100+ $60.75 **N Female to BNC Female Bulkhead-Mounting Hole G01** Max. Freq. 4 GHz **Model No: PE9540**	 PRICE 1-24 $67.81 25-49 $64.42 50-99 $61.03 100+ $58.32 **N Female to C Male** VSWR 1.25:1 to 11 GHz **Model No: PE9295**	 PRICE 1-24 $99.08 25-49 $94.13 50-99 $89.17 100+ $85.21 **N Female to C Female** **Model No: PE9539**	 PRICE 1-24 $45.74 25-49 $43.45 50-99 $41.17 100+ $39.34 **N Female to 75 Ohm F Male** VSWR 1.3:1 to 250 MHz **Model No: PE9389**	 PRICE 1-9 $191.83 10-24 $182.24 25-49 $172.65 50+ $164.97 **N Female to GR874 Sexless** **Model No: PE9258**
5	 PRICE 1-24 $58.30 25-49 $55.39 50-99 $52.47 100+ $50.14 **N Female to HN Male** VSWR 1.3:1 to 3 GHz **Model No: PE9194**	 PRICE 1-24 $83.15 25-49 $78.99 50-99 $74.84 100+ $71.51 **N Female to HN Female** **Model No: PE9360**	 PRICE 1-24 $122.86 25-49 $116.72 50-99 $110.57 100+ $105.66 **N Female to HN Female 4 Hole Flange-Mounting Hole A08** **Model No: PE9553**	 PRICE 1-9 $314.82 10-24 $299.08 25-49 $283.34 50+ $270.75 **N Female to LC Male** Max. Freq. 1,000 MHz **Model No: PE9237**	 PRICE 1-9 $292.63 10-24 $278.00 25-49 $263.37 50+ $251.66 **N Female to LC Female** **Model No: PE9298**
6	 PRICE 1-24 $109.97 25-49 $105.57 50-99 $102.27 100+ $100.07 **N Female to MCX Plug** Max. Freq. 6 GHz **Model No: PE9463**	 PRICE 1-9 $138.58 10-24 $131.65 25-49 $124.72 50+ $119.18 **N Female to MCX Jack** Max. Freq. 6 GHz **Model No: PE9462**	 PRICE 1-24 $28.77 25-49 $27.33 50-99 $25.89 100+ $24.74 **N Female to Mini UHF Male** VSWR 1.5:1 to 2.5 GHz **Model No: PE9183**	 PRICE 1-9 $118.57 10-24 $112.64 25-49 $106.71 50+ $101.97 **N Female to SC Male** VSWR 1.25:1 to 11 GHz **Model No: PE9277**	 PRICE 1-9 $119.05 10-24 $113.10 25-49 $107.15 50+ $102.38 **N Female to SC Female** VSWR 1.25:1 to 11 GHz **Model No: PE9292**
7	Low PIM PRICE 1-24 $53.30 25-49 $50.64 50-99 $47.97 100+ $45.84 **N Female to SMA Male** VSWR 1.2:1 to 6 GHz **Model No: PE91178**	 PRICE 1-24 $78.35 25-49 $74.43 50-99 $70.52 100+ $67.38 **N Female to SMB Plug** **Model No: PE9316**	 PRICE 1-24 $78.35 25-49 $74.43 50-99 $70.52 100+ $67.38 **N Female to SMB Jack** **Model No: PE9315**	 PRICE 1-24 $111.53 25-49 $105.95 50-99 $100.38 100+ $95.92 **N Female to SMC Plug** **Model No: PE9320**	 PRICE 1-24 $90.90 25-49 $86.36 50-99 $81.81 100+ $78.17 **N Female to SMC Jack** **Model No: PE9319**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	PRICE 1-24 $21.40 25-49 $20.33 50-99 $19.26 100+ $18.40 **N Female to TNC Male** VSWR 1.3:1 to 6 GHz **Model No:** PE9089	PRECISION PRICE 1-24 $150.28 25-49 $139.76 50-99 $129.24 100+ $120.22 **N Female to TNC Male** VSWR 1.2:1 to 18 GHz **Model No:** PE91506	PRICE 1-24 $70.42 25-49 $66.90 50-99 $63.38 100+ $60.56 **N Female to TNC Male Right Angle** VSWR 1.5:1 to 6 GHz **Model No:** PE9263	PRICE 1-24 $31.78 25-49 $30.19 50-99 $28.60 100+ $27.33 **N Female to TNC Female** VSWR 1.5:1 to 3 GHz **Model No:** PE9131	PRECISION PRICE 1-9 $201.38 10-24 $191.31 25-49 $181.24 50+ $173.19 **N Female to TNC Female** VSWR 1.15:1 to 18 GHz **Model No:** PE9449
2	PRICE 1-24 $96.08 25-49 $91.28 50-99 $86.47 100+ $82.63 **N Female to TNC Female 4 Hole Flange-Mounting Hole A05** **Model No:** PE9552	PRICE 1-24 $51.66 25-49 $49.08 50-99 $46.49 100+ $44.43 **N Female to TNC Female Bulkhead** VSWR 1.35:1 to 10 GHz **Model No:** PE9482	PRECISION PRICE 1-9 $159.87 10-24 $151.88 25-49 $143.88 50+ $137.49 **N Female to TNC Female 4 Hole Flange-Mounting Hole A05** VSWR 1.15:1 to 18 GHz **Model No:** PE9450	PRICE 1-24 $34.60 25-49 $32.87 50-99 $31.14 100+ $29.76 **N Female to UHF Male** VSWR 1.3:1 to 300 MHz **Model No:** PE9112	PRICE 1-24 $41.19 25-49 $39.13 50-99 $37.07 100+ $35.42 **N Female to UHF Female** Max. Freq. 1,000 MHz **Model No:** PE9385
3	***Reverse Polarity N Between Series*** →	PRICE 1-24 $52.47 25-49 $49.85 50-99 $47.22 100+ $45.12 **N Male to Rev. Pol. TNC Female** VSWR 1.3:1 to 6 GHz **Model No:** PE9730	PRICE 1-24 $51.30 25-49 $48.74 50-99 $46.17 100+ $44.12 **N Female to Rev. Pol. TNC Male** **Model No:** PE9731	***QMA In-Series*** →	PRICE 1-24 $60.78 25-49 $57.74 50-99 $54.70 100+ $52.27 **Snap-On QMA Male to Snap-On QMA Male** VSWR 1.08:1 to 6 GHz **Model No:** PE91341
4	PRICE 1-24 $36.89 25-49 $35.05 50-99 $33.20 100+ $31.73 **Snap-On QMA Male to Snap-On QMA Female** VSWR 1.12:1 to 6 GHz **Model No:** PE91342	PRICE 1-9 $175.92 10-24 $167.12 25-49 $158.33 50+ $151.29 **Snap-On QMA Female to Snap-On QMA Female** VSWR 1.08:1 to 6 GHz **Model No:** PE91343	***QMA Between Series*** →	PRICE 1-9 $181.89 10-24 $172.80 25-49 $163.70 50+ $156.43 **Snap-On QMA Male to Snap-On SMA Male** VSWR 1.18:1 to 6 GHz **Model No:** PE91344	PRICE 1-24 $65.57 25-49 $62.29 50-99 $59.01 100+ $56.39 **Snap-On QMA Male to SMA Female** VSWR 1.18:1 to 6 GHz **Model No:** PE91345
5	PRICE 1-24 $52.09 25-49 $49.49 50-99 $46.88 100+ $44.80 **Snap-On QMA Female to SMA Male** VSWR 1.18:1 to 6 GHz **Model No:** PE91346	PRICE 1-9 $111.59 10-24 $106.01 25-49 $100.43 50+ $95.97 **Snap-On QMA Female to Snap-On SMA Female** VSWR 1.18:1 to 6 GHz **Model No:** PE91347	***SC In-Series*** →	PRICE 1-9 $121.07 10-24 $115.02 25-49 $108.96 50+ $104.12 **SC Male to SC Male** **Model No:** PE9403	PRICE 1-24 $90.62 25-49 $86.09 50-99 $81.56 100+ $77.93 **SC Male to SC Female** **Model No:** PE9572
6	PRICE 1-9 $175.25 10-24 $166.49 25-49 $157.73 50+ $150.72 **SC Male to SC Female Right Angle** **Model No:** PE9405	PRICE 1-9 $284.24 10-24 $270.03 25-49 $255.82 50+ $244.45 **SC Female to SC Male Tee** **Model No:** PE9225	PRICE 1-9 $127.39 10-24 $121.02 25-49 $114.65 50+ $109.56 **SC Female to SC Female** VSWR 1.25:1 to 11 GHz **Model No:** PE9404	PRICE 1-9 $163.82 10-24 $155.63 25-49 $147.44 50+ $140.89 **SC Female to SC Female Bulkhead** **Model No:** PE9573	***SC Between Series*** →
7	PRICE 1-24 $61.07 25-49 $58.02 50-99 $54.96 100+ $52.52 **SC Male to BNC Male** **Model No:** PE9568	PRICE 1-24 $81.97 25-49 $77.87 50-99 $73.77 100+ $70.49 **SC Female to BNC Female** **Model No:** PE9571	***SHV In-Series*** →	PRICE 1-9 $137.84 10-24 $130.95 25-49 $124.06 50+ $118.54 **SHV Plug to SHV Jack** **Model No:** PE9749	PRICE 1-24 $89.96 25-49 $85.46 50-99 $80.96 100+ $77.37 **SHV Plug to SHV Jack Right Angle** **Model No:** PE9338

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $104.33 25-49 $99.11 50-99 $93.90 100+ $89.72 **SHV Jack to SHV Plug Tee** VSWR 1.2:1 to 300 MHz **Model No: PE9249**	 PRICE 1-24 $46.18 25-49 $43.87 50-99 $41.56 100+ $39.71 **SHV Jack to SHV Jack** VSWR 1.3:1 to 300 MHz **Model No: PE9337**	 PRICE 1-24 $70.37 25-49 $66.85 50-99 $63.33 100+ $60.52 **SHV Jack to SHV Jack Bulkhead** Max. Freq. 300 MHz **Model No: PE9336**	***SMA In-Series*** →	 PRICE 1-24 $19.29 25-49 $18.33 50-99 $17.36 100+ $16.59 **SMA Male to SMA Male** VSWR 1.23:1 to 18 GHz **Model No: PE91135**
2	 PRICE 1-24 $74.01 25-49 $70.31 50-99 $66.61 PRECISION 100+ $63.65 **SMA Male to SMA Male** VSWR 1.2:1 to 27 GHz **Model No: PE9505**	 PRICE 1-24 $81.98 25-49 $77.88 50-99 $73.78 NEW 100+ $70.50 **SMA Male to SMA Male Radius Right Angle** VSWR 1.35:1 to 26 GHz **Model No: PE91496**	 PRICE 1-24 $83.73 25-49 $79.54 50-99 $75.36 NEW 100+ $72.01 **SMA Male to SMA Male Radius Right Angle** VSWR 1.35:1 to 26 GHz **Model No: PE91497**	 PRICE 1-24 $54.33 25-49 $51.61 50-99 $48.90 100+ $46.72 **SMA Male to SMA Male Right Angle** VSWR 1.5:1 to 12.4 GHz **Model No: PE9418**	 PRICE 1-24 $85.79 25-49 $81.50 50-99 $77.21 100+ $73.78 **SMA Male to SMA Male Tee** **Model No: PE9379**
3	 PRICE 1-24 $105.22 25-49 $99.96 50-99 $94.70 PRECISION 100+ $90.49 **SMA Male to SMA Male Miter Right Angle** VSWR 1.15:1 to 27 GHz **Model No: PE91151**	 PRICE 1-24 $94.56 25-49 $89.83 50-99 $85.10 100+ $81.32 **SMA Male to SMA Male Miter Right Angle** VSWR 1.35:1 to 27 GHz **Model No: PE9642**	 PRICE 1-9 $221.64 10-24 $212.77 25-49 $206.13 50+ $201.69 **SMA Male to SMA Male 4 Hole Flange-Mounting Hole A01** VSWR 1.2:1 to 18 GHz **Model No: PE9669**	 PRICE 1-24 $33.57 25-49 $31.89 50-99 $30.21 NEW 100+ $28.87 **SMA Male to SMA Male** VSWR 1.2:1 to 27 GHz **Model No: PE91535**	 PRICE 1-24 $28.29 25-49 $26.88 50-99 $25.46 100+ $24.33 **SMA Male to SMA Female** VSWR 1.25:1 to 18 GHz **Model No: PE9103**
4	 PRICE 1-24 $63.16 25-49 $58.74 50-99 $54.32 PRECISION NEW 100+ $50.53 **SMA Male to SMA Female** VSWR 1.2:1 to 27 GHz **Model No: PE9506**	 PRICE 1-24 $32.00 25-49 $30.40 50-99 $28.80 100+ $27.52 **QD SMA Male to SMA Female** **Model No: PE9546**	 PRICE 1-24 $53.31 25-49 $50.64 50-99 $47.98 PRECISION 100+ $45.85 **SMA Male to SMA Female** VSWR 1.2:1 to 18 GHz **Model No: PE9694**	 PRICE 1-9 $149.17 10-24 $141.71 25-49 $134.25 PRECISION 50+ $128.29 **QD SMA Male to SMA Female** VSWR 1.14:1 to 18 GHz **Model No: PE9774**	 PRICE 1-24 $59.11 25-49 $56.15 50-99 $53.20 100+ $50.83 **SMA Male to SMA Female Radius Right Angle** VSWR 1.2:1 to 18 GHz **Model No: PE91492**
5	 PRICE 1-24 $62.16 25-49 $59.05 50-99 $55.94 100+ $53.46 **SMA Male to SMA Female Radius Right Angle** VSWR 1.2:1 to 18 GHz **Model No: PE91493**	 PRICE 1 $89.31 **SMA Male to SMA Female Radius Right Angle** VSWR 1.25:1 to 18 GHz **Model No: PE91155**	 PRICE 1-24 $78.82 25-49 $74.88 50-99 $70.94 100+ $67.79 **SMA Male to SMA Female Radius Right Angle** VSWR 1.55:1 to 26.5 GHz **Model No: PE91222**	 PRICE 1-24 $31.77 25-49 $30.18 50-99 $28.59 100+ $27.32 **SMA Male to SMA Female Right Angle** VSWR 1.23:1 to 12.4 GHz **Model No: PE9068**	 PRICE 1-24 $99.91 25-49 $94.91 50-99 $89.92 PRECISION 100+ $85.92 **SMA Male to SMA Female 45 Degree Right** VSWR 1.3:1 to 27 GHz **Model No: PE91332**
6	 PRICE 1-24 $85.64 25-49 $81.36 50-99 $77.08 100+ $73.65 **SMA Male to SMA Female Tee** VSWR 2.25:1 to 6 GHz **Model No: PE9247**	 PRICE 1-24 $55.77 25-49 $52.98 50-99 $50.19 100+ $47.96 **SMA Male to SMA Female Bulkhead** VSWR 1.3:1 to 18 GHz **Model No: PE9621**	 PRICE 1-24 $83.81 25-49 $77.94 50-99 $72.08 NEW 100+ $67.05 **SMA Male to SMA Female 4 Hole Flange** VSWR 1.2:1 to 18 GHz **Model No: PE91453**	 PRICE 1-24 $27.66 25-49 $26.28 50-99 $24.89 100+ $23.79 **Push-On SMA Male to SMA Female Bulkhead** VSWR 1.23:1 to 18 GHz **Model No: PE91321**	 PRICE 1-24 $69.84 25-49 $66.35 50-99 $62.86 PRECISION 100+ $60.06 **SMA Male to SMA Female Miter Right Angle** VSWR 1.2:1 to 27 GHz **Model No: PE91504**
7	 PRICE 1-24 $50.29 25-49 $47.78 50-99 $45.26 100+ $43.25 **SMA Female to SMA Male Tee** Max. Freq. 6 GHz **Model No: PE9182**	 PRICE 1-24 $19.14 25-49 $18.18 50-99 $17.23 100+ $16.46 **SMA Female to SMA Female** VSWR 1.25:1 to 18 GHz **Model No: PE9070**	 PRICE 1-24 $34.76 25-49 $33.02 50-99 $31.28 100+ $29.89 **SMA Female to SMA Female** VSWR 1.23:1 to 18 GHz **Model No: PE9380**	 PRICE 1-24 $65.03 25-49 $61.78 50-99 $58.53 PRECISION 100+ $55.93 **SMA Female to SMA Female** VSWR 1.2:1 to 27 GHz **Model No: PE9507**	 PRICE 1-24 $46.39 25-49 $44.07 50-99 $41.75 PRECISION 100+ $39.90 **SMA Female to SMA Female** VSWR 1.15:1 to 18 GHz **Model No: PE9695**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 NEW PRICE 1-24 $82.56 25-49 $78.43 50-99 $74.30 100+ $71.00 **SMA Female to SMA Female Radius Right Angle** VSWR 1.25:1 to 18 GHz **Model No: PE91494**	 NEW PRICE 1-24 $84.73 25-49 $80.49 50-99 $76.26 100+ $72.87 **SMA Female to SMA Female Radius Right Angle** VSWR 1.25:1 to 18 GHz **Model No: PE91495**	 PRECISION NEW PRICE 1-24 $97.68 25-49 $90.84 50-99 $84.00 100+ $78.14 **SMA Female to SMA Female Right Angle** VSWR 1.15:1 to 27 GHz **Model No: PE91153**	 PRICE 1-24 $61.31 25-49 $58.24 50-99 $55.18 100+ $52.73 **SMA Female to SMA Female Right Angle** **Model No: PE9485**	 PRICE 1-24 $69.03 25-49 $65.58 50-99 $62.13 100+ $59.37 **SMA Female to SMA Female Tee** Max. Freq. 6 GHz **Model No: PE9246**
2	 PRICE 1-24 $64.73 25-49 $61.49 50-99 $58.26 100+ $55.67 **SMA Female to SMA Female Bulkhead-Mounting Hole B02** VSWR 1.23:1 to 18 GHz **Model No: PE9014**	 PRICE 1-24 $20.50 25-49 $19.48 50-99 $18.45 100+ $17.63 **SMA Female to SMA Female Bulkhead** VSWR 1.25:1 to 18 GHz **Model No: PE91258**	 PRICE 1-9 $113.12 10-24 $107.46 25-49 $101.81 50+ $97.28 **SMA Female to SMA Female Bulkhead-Mounting Hole B02** VSWR 1.3:1 to 26.5 GHz **Model No: PE9508**	 PRECISION PRICE 1-24 $47.48 25-49 $45.11 50-99 $42.73 100+ $40.83 **SMA Female to SMA Female Bulkhead-Mounting Hole B02** VSWR 1.15:1 to 18 GHz **Model No: PE9620**	 PRICE 1-9 $46.57 10-24 $44.24 25-49 $41.91 50+ $40.05 **SMA Female to SMA Female Bulkhead** VSWR 1.35:1 to 18 GHz **Model No: PE91393**
3	 PRICE 1-24 $49.03 25-49 $46.58 50-99 $44.13 100+ $42.17 **SMA Female to SMA Female Bulkhead** VSWR 1.4:1 to 18 GHz **Model No: PE9184**	 PRICE 1-24 $37.17 25-49 $35.31 50-99 $33.45 100+ $31.97 **SMA Female to SMA Female Bulkhead** VSWR 1.25:1 to 12.4 GHz **Model No: PE9067**	 PRICE 1-24 $67.10 25-49 $63.75 50-99 $60.39 100+ $57.71 **SMA Female to SMA Female 4 Hole Flange-Mounting Hole A01** VSWR 1.25:1 to 18 GHz **Model No: PE9312**	 PRICE 1-24 $95.98 25-49 $91.18 50-99 $86.38 100+ $82.54 **SMA Female to SMA Female 4 Hole Flange-Mounting Hole A01** VSWR 1.25:1 to 18 GHz **Model No: PE9670**	 PRICE 1-24 $25.90 25-49 $24.61 50-99 $23.31 100+ $22.27 **SMA Female to SMA Female Bulkhead** VSWR 1.23:1 to 18 GHz **Model No: PE9184NH**
4	 PRICE 1-24 $21.44 25-49 $20.37 50-99 $19.30 100+ $18.44 **SMA Female to SMA Female 2 Hole Flange** VSWR 1.25:1 to 18 GHz **Model No: PE91290**	 PRECISION NEW PRICE 1-24 $31.77 25-49 $30.18 50-99 $28.59 100+ $27.32 **SMA Female to SMA Female** VSWR 1.2:1 to 27 GHz **Model No: PE91549**	 NEW PRICE 1-24 $86.38 25-49 $82.06 50-99 $77.74 100+ $74.29 **SMA Female to SMA Female Miter Right Angle** VSWR 1.2:1 to 27 GHz **Model No: PE91176**	***Reverse Polarity SMA In-Series***	 PRICE 1-24 $44.91 25-49 $42.66 50-99 $40.42 100+ $38.62 **SMA Male to Rev. Pol. SMA Male** VSWR 1.2:1 to 18 GHz **Model No: PE91259**
5	 PRICE 1-24 $69.40 25-49 $65.93 50-99 $62.46 100+ $59.68 **QD SMA Male to Rev. Pol. SMA Female** VSWR 1.25:1 to 18 GHz **Model No: PE91265**	 PRICE 1-24 $43.07 25-49 $40.92 50-99 $38.76 100+ $37.04 **SMA Male to Rev. Pol. SMA Female** VSWR 1.25:1 to 18 GHz **Model No: PE9534**	 PRICE 1-24 $47.56 25-49 $45.18 50-99 $42.80 100+ $40.90 **SMA Male to Rev. Pol. SMA Female Right Angle** VSWR 1.23:1 to 12.4 GHz **Model No: PE91264**	 PRICE 1-24 $23.91 25-49 $22.71 50-99 $21.52 100+ $20.56 **SMA Female to Rev. Pol. SMA Male** VSWR 1.25:1 to 18 GHz **Model No: PE9533**	 PRICE 1-24 $38.26 25-49 $36.35 50-99 $34.43 100+ $32.90 **SMA Female to Rev. Pol. SMA Female** VSWR 1.2:1 to 18 GHz **Model No: PE91260**
6	 PRICE 1-24 $115.25 25-49 $109.49 50-99 $103.73 100+ $99.12 **QD Rev. Pol. SMA Male to SMA Male** VSWR 1.25:1 to 18 GHz **Model No: PE91266**	 PRICE 1-24 $76.27 25-49 $72.46 50-99 $68.64 100+ $65.59 **QD Rev. Pol. SMA Male to SMA Female** VSWR 1.25:1 to 18 GHz **Model No: PE91267**	 PRICE 1-24 $38.97 25-49 $37.02 50-99 $35.07 100+ $33.51 **Rev. Pol. SMA Male to SMA Female Right Angle** VSWR 1.23:1 to 12.4 GHz **Model No: PE91263**	 PRICE 1-24 $46.26 25-49 $43.95 50-99 $41.63 100+ $39.78 **Rev. Pol. SMA Male to Rev. Pol. SMA Male** VSWR 1.2:1 to 18 GHz **Model No: PE91261**	 PRICE 1-24 $57.04 25-49 $54.19 50-99 $51.34 100+ $49.05 **Rev. Pol. SMA Male to Rev. Pol. SMA Male** VSWR 1.35:1 to 6 GHz **Model No: PE91330**
7	 PRICE 1-24 $69.40 25-49 $65.93 50-99 $62.46 100+ $59.68 **QD Rev. Pol. SMA Male to Rev. Pol. SMA Female** VSWR 1.25:1 to 18 GHz **Model No: PE91268**	 PRICE 1-24 $56.92 25-49 $54.07 50-99 $51.23 100+ $48.95 **Rev. Pol. SMA Male to Rev. Pol. SMA Female** VSWR 1.35:1 to 6 GHz **Model No: PE91331**	 PRICE 1-24 $38.26 25-49 $36.35 50-99 $34.43 100+ $32.90 **Rev. Pol. SMA Male to Rev. Pol. SMA Female Right Angle** VSWR 1.25:1 to 6 GHz **Model No: PE9594**	 PRICE 1-24 $46.26 25-49 $43.95 50-99 $41.63 100+ $39.78 **Rev. Pol. SMA Female to Rev. Pol. SMA Female** VSWR 1.2:1 to 18 GHz **Model No: PE91262**	 PRICE 1-24 $37.53 25-49 $35.65 50-99 $33.78 100+ $32.28 **Rev. Pol. SMA Female to Rev. Pol. SMA Female** VSWR 1.35:1 to 6 GHz **Model No: PE91334**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $54.07 25-49 $51.37 50-99 $48.66 100+ $46.50 **Rev. Pol. SMA Female to Rev. Pol. SMA Female Bulkhead-Mounting Hole B02** VSWR 1.25:1 to 18 GHz **Model No: PE9593**	 PRICE 1-24 $47.63 25-49 $45.25 50-99 $42.87 100+ $40.96 **Rev. Pol. SMA Female to Rev. Pol. SMA Female 2 Hole Flange** VSWR 1.2:1 to 18 GHz **Model No: PE91270**	 PRICE 1-24 $49.20 25-49 $46.74 50-99 $44.28 100+ $42.31 **Rev. Pol. SMA Female to Rev. Pol. SMA Female 4 Hole Flange** VSWR 1.2:1 to 18 GHz **Model No: PE91269**	***Reverse Thread SMA In-Series*** →	 PRICE 1-24 $54.29 25-49 $51.58 50-99 $48.86 100+ $46.69 **SMA Male to Reverse Thread SMA Female** **Model No: PE9682**
2	 PRICE 1-24 $62.53 25-49 $59.40 50-99 $56.28 100+ $53.78 **SMA Female to Reverse Thread SMA Male** **Model No: PE9683**	***SMA Between Series*** →	 PRICE 1-24 $117.37 25-49 $111.50 50-99 $105.63 100+ $100.94 **SMA Male to 1.0/2.3 Plug** **Model No: PE9692**	 PRICE 1-24 $97.95 25-49 $93.05 50-99 $88.16 100+ $84.24 **SMA Male to 1.0/2.3 Jack** **Model No: PE9690**	 PRICE 1-9 $217.64 10-24 $206.76 25-49 $195.88 50+ $187.17 **SMA Male to 1.85mm Male** VSWR 1.3:1 to 18 GHz **Model No: PE9727**
3	 PRICE 1-9 $225.66 10-24 $214.38 25-49 $203.09 50+ $194.07 **SMA Male to 1.85mm Female** VSWR 1.3:1 to 18 GHz **Model No: PE9728**	 PRICE 1-9 $211.98 10-24 $201.38 25-49 $190.78 PRECISION 50+ $182.30 **SMA Male to 2.4mm Male** VSWR 1.2:1 to 26.5 GHz **Model No: PE9653**	 PRICE 1-9 $233.32 10-24 $221.65 25-49 $209.99 PRECISION 50+ $200.66 **SMA Male to 2.4mm Female** VSWR 1.2:1 to 26.5 GHz **Model No: PE9654**	 PRICE 1-9 $218.45 10-24 $207.53 25-49 $196.61 PRECISION 50+ $187.87 **SMA Male to 2.92mm Male** VSWR 1.2:1 to 26.5 GHz **Model No: PE91010**	 PRICE 1-9 $214.24 10-24 $203.53 25-49 $192.82 PRECISION 50+ $184.25 **SMA Male to 2.92mm Female** VSWR 1.2:1 to 26.5 GHz **Model No: PE91008**
4	 PRICE 1-9 $215.61 10-24 $204.83 25-49 $194.05 50+ $185.42 **SMA Male to 3.5mm Male** VSWR 1.25:1 to 18 GHz **Model No: PE9722**	 PRICE 1-9 $164.15 10-24 $155.94 25-49 $147.74 NEW 50+ $141.17 **SMA Male to 3.5mm Female** VSWR 1.2:1 to 27 GHz **Model No: PE91536**	 PRICE 1-4 $534.33 5-9 $507.61 10-24 $480.90 PRECISION 25+ $459.52 **SMA Male to 7mm Sexless** VSWR 1.15:1 to 18 GHz **Model No: PE9215**	 PRICE 1-4 Call 5-9 Call 10-24 Call 25+ Call **SMA Male to 7/16 DIN Female** **Model No: PE9411**	 PRICE 1-24 $44.95 25-49 $42.70 50-99 $40.46 100+ $38.66 **SMA Male to BNC Male** Max. Freq. 4 GHz **Model No: PE9072**
5	 PRICE 1-24 $115.32 25-49 $109.55 50-99 $103.79 100+ $99.18 **SMA Male to BNC Male** VSWR 1.25:1 to 8 GHz **Model No: PE9493**	 PRICE 1-24 $28.40 25-49 $26.98 50-99 $25.56 100+ $24.42 **SMA Male to BNC Female** VSWR 1.3:1 to 4 GHz **Model No: PE9074**	 PRICE 1-9 $150.97 10-24 $143.42 25-49 $135.87 50+ $129.83 **SMA Male to BNC Female** VSWR 1.25:1 to 8 GHz **Model No: PE9495**	 PRICE 1-24 $35.98 25-49 $34.18 50-99 $32.38 100+ $30.94 **SMA Male to 75 Ohm F Female** Max. Freq. 2 GHz **Model No: PE91003**	 PRICE 1-24 $23.51 25-49 $22.33 50-99 $21.16 100+ $20.22 **SMA Male to FME Jack** **Model No: PE9707**
6	 PRICE 1-9 $247.78 10-24 $235.39 25-49 $223.00 50+ $213.09 **SMA Male to GR874 Sexless** **Model No: PE9259**	 PRICE 1-24 $94.22 25-49 $89.51 50-99 $84.80 100+ $81.03 **SMA Male to HN Male** VSWR 1.4:1 to 4 GHz **Model No: PE91448**	 PRICE 1-9 $140.65 10-24 $133.62 25-49 $126.59 50+ $120.96 **SMA Male to HN Female** **Model No: PE9256**	 PRICE 1-24 $115.40 25-49 $109.63 50-99 $103.86 100+ $99.24 **SMA Male to MCX Plug** **Model No: PE9473**	 PRICE 1-24 $104.58 25-49 $99.35 50-99 $94.12 100+ $89.94 **SMA Male to MCX Jack** **Model No: PE9472**
7	 PRICE 1-24 $90.72 25-49 $86.18 50-99 $81.65 100+ $78.02 **SMA Male to Full Detent Mini SMP Male** VSWR 1.2:1 to 18 GHz **Model No: PE91302**	 PRICE 1-24 $102.28 25-49 $97.17 50-99 $92.05 100+ $87.96 **SMA Male to Smooth Bore Mini SMP Male** VSWR 1.2:1 to 18 GHz **Model No: PE91303**	 PRICE 1-9 $191.34 10-24 $181.77 25-49 $172.21 PRECISION 50+ $164.55 **SMA Male to Full Detent Mini SMP Male** VSWR 1.2:1 to 26.5 GHz **Model No: PE91052**	 PRICE 1-24 $92.42 25-49 $87.80 50-99 $83.18 100+ $79.48 **SMA Male to Mini SMP Female** VSWR 1.2:1 to 18 GHz **Model No: PE91304**	 PRICE 1-9 $233.30 10-24 $221.64 25-49 $209.97 PRECISION 50+ $200.64 **SMA Male to Mini SMP Female** VSWR 1.2:1 to 26.5 GHz **Model No: PE91103**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-9 $129.75 10-24 $123.26 25-49 $116.78 50+ $111.59 **SMA Male to MMCX Plug** **Model No: PE9476**	 PRICE 1-24 $96.80 25-49 $91.96 50-99 $87.12 100+ $83.25 **SMA Male to MMCX Jack** **Model No: PE9478**	 PRICE 1-9 $252.30 10-24 $239.69 25-49 $227.07 50+ $216.98 **SMA Male to Snap-On MMBX Plug** VSWR 1.2:1 to 12.4 GHz **Model No: PE91360**	 PRICE 1-9 $187.57 10-24 $178.19 25-49 $168.81 50+ $161.31 **SMA Male to Snap-On MMBX Jack** VSWR 1.08:1 to 12.4 GHz **Model No: PE91362**	 PRICE 1-24 $24.85 25-49 $23.61 50-99 $22.37 100+ $21.37 **SMA Male to N Male** VSWR 1.3:1 to 11 GHz **Model No: PE9080**
2	 PRICE 1-9 $140.50 10-24 $133.48 25-49 $126.45 PRECISION 50+ $120.83 **SMA Male to N Male** VSWR 1.15:1 to 18 GHz **Model No: PE9431**	 PRICE 1-9 $144.84 10-24 $137.60 25-49 $130.36 PRECISION 50+ $124.56 **SMA Male to N Male** **4 Hole Flange-Mounting Hole A05** VSWR 1.15:1 to 18 GHz **Model No: PE9499**	 PRICE 1-24 $23.31 25-49 $22.14 50-99 $20.98 100+ $20.05 **SMA Male to N Female** VSWR 1.3:1 to 11 GHz **Model No: PE9082**	 PRICE 1-24 $104.18 25-49 $98.97 50-99 $93.76 PRECISION 100+ $89.59 **SMA Male to N Female** VSWR 1.15:1 to 18 GHz **Model No: PE9433**	 PRICE 1-9 $187.66 10-24 $178.28 25-49 $168.89 PRECISION 50+ $161.39 **SMA Male to N Female Bulkhead** VSWR 1.15:1 to 18 GHz **Model No: PE9487**
3	 PRICE 1-24 $103.44 25-49 $98.27 50-99 $93.10 100+ $88.96 **SMA Male to N Female** **4 Hole Flange** VSWR 1.4:1 to 18 GHz **Model No: PE9105**	 PRICE 1-9 $199.14 10-24 $189.18 25-49 $179.23 PRECISION 50+ $171.26 **SMA Male to N Female** **4 Hole Flange** VSWR 1.15:1 to 18 GHz **Model No: PE9497**	 PRICE 1-9 $181.86 10-24 $172.77 25-49 $163.67 PRECISION 50+ $156.40 **SMA Male to N Female Bulkhead** VSWR 1.15:1 to 18 GHz **Model No: PE9488**	 PRICE 1-24 $23.72 25-49 $22.77 50-99 $22.06 100+ $21.59 **Push-On SMA Male to SMA Female** VSWR 1.5:1 to 18 GHz **Model No: PE91336**	 PRICE 1-24 $90.68 25-49 $86.15 50-99 $81.61 100+ $77.98 **SMA Male to SMB Plug** VSWR 1.25:1 to 4 GHz **Model No: PE9144**
4	 PRICE 1-24 $24.84 25-49 $23.60 50-99 $22.36 100+ $21.36 **SMA Male to SMB Jack** VSWR 1.25:1 to 4 GHz **Model No: PE9145**	 PRICE 1-24 $72.20 25-49 $68.59 50-99 $64.98 100+ $62.09 **SMA Male to SMC Plug** Max. Freq. 10 GHz **Model No: PE9148**	 PRICE 1-24 $61.70 25-49 $58.62 50-99 $55.53 100+ $53.06 **SMA Male to SMC Jack** VSWR 1.2:1 to 10 GHz **Model No: PE9149**	 PRICE 1-24 $72.93 25-49 $69.28 50-99 $65.64 100+ $62.72 **SMA Male to Full Detent SMP Male** VSWR 1.2:1 to 18 GHz **Model No: PE91309**	 PRICE 1-24 $71.61 25-49 $68.03 50-99 $64.45 100+ $61.58 **SMA Male to Limited Detent SMP Male** VSWR 1.2:1 to 18 GHz **Model No: PE91310**
5	 PRICE 1-24 $71.61 25-49 $68.03 50-99 $64.45 100+ $61.58 **SMA Male to Smooth Bore SMP Male** VSWR 1.2:1 to 18 GHz **Model No: PE91311**	 PRICE 1-9 $128.61 10-24 $122.18 25-49 $115.75 PRECISION 50+ $110.60 **SMA Male to Full Detent SMP Male** VSWR 1.2:1 to 26.5 GHz **Model No: PE91063**	 PRICE 1-9 $170.39 10-24 $161.87 25-49 $153.35 PRECISION 50+ $146.54 **SMA Male to Limited Detent SMP Male** VSWR 1.2:1 to 18 GHz **Model No: PE9511**	 PRICE 1-24 $72.93 25-49 $69.28 50-99 $65.64 100+ $62.72 **SMA Male to SMP Female** VSWR 1.2:1 to 18 GHz **Model No: PE91312**	 PRICE 1-9 $159.64 10-24 $151.66 25-49 $143.68 PRECISION 50+ $137.29 **SMA Male to SMP Female** VSWR 1.2:1 to 26.5 GHz **Model No: PE91062**
6	 PRICE 1-9 $194.92 10-24 $185.17 25-49 $175.43 PRECISION 50+ $167.63 **SMA Male to SMP Female** VSWR 1.2:1 to 18 GHz **Model No: PE9513**	 PRICE 1-24 $102.21 25-49 $97.10 50-99 $91.99 100+ $87.90 **SMA Male to SSMA Male** VSWR 1.25:1 to 26.5 GHz **Model No: PE9187**	 PRICE 1-24 $67.36 25-49 $63.99 50-99 $60.62 100+ $57.93 **SMA Male to SSMA Female** VSWR 1.4:1 to 18 GHz **Model No: PE9063**	 PRICE 1-24 $95.54 25-49 $90.76 50-99 $85.99 100+ $82.16 **SMA Male to SSMB Jack** **Model No: PE9401**	 PRICE 1-24 $44.70 25-49 $42.47 50-99 $40.23 100+ $38.44 **SMA Male to TNC Male** VSWR 1.3:1 to 11 GHz **Model No: PE9076**
7	 PRICE 1-9 $139.58 10-24 $132.60 25-49 $125.62 50+ $120.04 **SMA Male to TNC Male** VSWR 1.25:1 to 18 GHz **Model No: PE9439**	 PRICE 1-24 $46.76 25-49 $44.42 50-99 $42.08 100+ $40.21 **SMA Male to TNC Female** VSWR 1.3:1 to 11 GHz **Model No: PE9078**	 PRICE 1-24 $111.78 25-49 $103.96 50-99 $96.13 100+ $89.42 **SMA Male to TNC Female** VSWR 1.2:1 to 18 GHz **Model No: PE91507**	 PRICE 1-24 $97.25 25-49 $92.39 50-99 $87.53 100+ $83.64 **SMA Male to TNC Female** **4 Hole Flange-Mounting Hole A04** VSWR 1.3:1 to 11 GHz **Model No: PE9384**	 PRICE 1-24 $49.16 25-49 $46.70 50-99 $44.24 100+ $42.28 **SMA Male to UHF Female** **Model No: PE9400**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $30.20 25-49 $28.69 50-99 $27.18 100+ $25.97 **SMA Male to UMCX Jack** VSWR 1.3:1 to 6 GHz **Model No: PE91007**	 PRICE 1-24 $98.85 25-49 $93.91 50-99 $88.97 100+ $85.01 **SMA Female to 1.0/2.3 Plug** **Model No: PE9691**	 PRICE 1-24 $86.17 25-49 $81.86 50-99 $77.55 100+ $74.11 **SMA Female to 1.0/2.3 Jack** **Model No: PE9693**	 PRICE 1-9 $213.55 10-24 $202.87 25-49 $192.20 50+ $183.65 **SMA Female to 1.85mm Male** VSWR 1.3:1 to 18 GHz **Model No: PE9726**	 PRICE 1-9 $220.53 10-24 $209.50 25-49 $198.48 50+ $189.66 **SMA Female to 1.85mm Female** VSWR 1.3:1 to 18 GHz **Model No: PE9729**
2	 PRICE 1-9 $218.61 10-24 $207.68 25-49 $196.75 50+ $188.00 **SMA Female to 2.4mm Male** VSWR 1.2:1 to 27 GHz **Model No: PE9655**	 PRECISION PRICE 1-9 $223.31 10-24 $212.14 25-49 $200.98 50+ $192.05 **SMA Female to 2.4mm Female** VSWR 1.2:1 to 26.5 GHz **Model No: PE9656**	 PRECISION PRICE 1-9 $210.15 10-24 $199.64 25-49 $189.14 50+ $180.73 **SMA Female to 2.92mm Male** VSWR 1.2:1 to 26.5 GHz **Model No: PE91009**	 PRECISION PRICE 1-9 $214.24 10-24 $203.53 25-49 $192.82 50+ $184.25 **SMA Female to 2.92mm Female** VSWR 1.2:1 to 26.5 GHz **Model No: PE91011**	 PRICE 1-9 $196.00 10-24 $186.20 25-49 $176.40 50+ $168.56 **SMA Female to 3.5mm Male** VSWR 1.2:1 to 27 GHz **Model No: PE9724**
3	 PRICE 1-9 $201.68 10-24 $191.60 25-49 $181.51 50+ $173.44 **SMA Female to 3.5mm Female** VSWR 1.2:1 to 27 GHz **Model No: PE9725**	 PRECISION PRICE 1-9 $235.28 10-24 $223.52 25-49 $211.75 50+ $202.34 **SMA Female to 7mm Sexless** VSWR 1.15:1 to 18 GHz **Model No: PE9214**	 PRECISION PRICE 1-4 $593.90 5-9 $564.21 10-24 $534.51 25+ $510.75 **SMA Female to 7mm Sexless 4 Hole Flange-Mounting Hole A05** VSWR 1.15:1 to 18 GHz **Model No: PE9327**	 Low PIM PRICE 1-24 $92.67 25-49 $88.04 50-99 $83.40 100+ $79.70 **SMA Female to 7/16 DIN Male** VSWR 1.09:1 to 7.5 GHz **Model No: PE91036**	 PRICE 1-9 $116.02 10-24 $110.22 25-49 $104.42 50+ $99.78 **SMA Female to 7/16 DIN Male** VSWR 1.25:1 to 6 GHz **Model No: PE91175**
4	 Low PIM PRICE 1-24 $93.44 25-49 $88.77 50-99 $84.10 100+ $80.36 **SMA Female to 7/16 DIN Female** Max. Freq. 8 GHz **Model No: PE91042**	 PRICE 1-24 $21.57 25-49 $20.49 50-99 $19.41 100+ $18.55 **SMA Female to BNC Male** VSWR 1.3:1 to 4 GHz **Model No: PE9073**	 PRICE 1-24 $82.17 25-49 $78.06 50-99 $73.95 100+ $70.67 **SMA Female to BNC Male** VSWR 1.25:1 to 8 GHz **Model No: PE9494**	 PRICE 1-24 $46.45 25-49 $44.13 50-99 $41.81 100+ $39.95 **SMA Female to BNC Female** VSWR 1.3:1 to 4 GHz **Model No: PE9075**	 PRICE 1-24 $115.32 25-49 $109.55 50-99 $103.79 100+ $99.18 **SMA Female to BNC Female** VSWR 1.25:1 to 8 GHz **Model No: PE9496**
5	 PRICE 1-24 $58.54 25-49 $55.61 50-99 $52.69 100+ $50.34 **SMA Female to BNC Female Bulkhead** Max. Freq. 4 GHz **Model No: PE9185**	 PRICE 1-24 $65.82 25-49 $62.53 50-99 $59.24 100+ $56.61 **SMA Female to BNC Female Bulkhead** Max. Freq. 4 GHz **Model No: PE9407**	 PRICE 1-24 $26.54 25-49 $25.21 50-99 $23.89 100+ $22.82 **SMA Female to 75 Ohm F Male** VSWR 1.5:1 to 500 MHz **Model No: PE91045**	 PRICE 1-24 $56.89 25-49 $54.05 50-99 $51.20 100+ $48.93 **SMA Female to 75 Ohm F Female** **Model No: PE91002**	 PRICE 1-24 $21.64 25-49 $20.56 50-99 $19.48 100+ $18.61 **SMA Female to FME Plug** **Model No: PE9703**
6	 PRICE 1-24 $27.97 25-49 $26.57 50-99 $25.17 100+ $24.05 **SMA Female to FME Jack** VSWR 1.3:1 to 900 MHz **Model No: PE9708**	 PRICE 1-9 $185.44 10-24 $176.17 25-49 $166.90 50+ $159.48 **SMA Female to GR874 Sexless** **Model No: PE9260**	 PRICE 1-24 $85.15 25-49 $80.89 50-99 $76.64 100+ $73.23 **SMA Female to HN Male** Max. Freq. 4 GHz **Model No: PE9253**	 PRICE 1-24 $69.81 25-49 $66.32 50-99 $62.83 100+ $60.04 **SMA Female to HN Female** **Model No: PE9255**	 PRICE 1-24 $83.93 25-49 $79.73 50-99 $75.54 100+ $72.18 **SMA Female to MCX Plug** **Model No: PE9471**
7	 PRICE 1-24 $82.52 25-49 $78.39 50-99 $74.27 100+ $70.97 **SMA Female to MCX Jack** **Model No: PE9470**	 PRICE 1-24 $92.42 25-49 $87.80 50-99 $83.18 100+ $79.48 **SMA Female to Full Detent Mini SMP Male** VSWR 1.2:1 to 18 GHz **Model No: PE91299**	 PRICE 1-24 $102.28 25-49 $97.17 50-99 $92.05 100+ $87.96 **SMA Female to Smooth Bore Mini SMP Male** VSWR 1.2:1 to 18 GHz **Model No: PE91300**	 PRICE 1-9 $175.00 10-24 $166.25 25-49 $157.50 50+ $150.50 **SMA Female to Full Detent Mini SMP Male** VSWR 1.2:1 to 26.5 GHz **Model No: PE91129**	 PRICE 1-24 $91.56 25-49 $86.98 50-99 $82.40 100+ $78.74 **SMA Female to Mini SMP Female** VSWR 1.2:1 to 18 GHz **Model No: PE91301**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 PRECISION 1-9 $157.83 10-24 $149.94 25-49 $142.05 50+ $135.73 **SMA Female to Mini SMP Female** VSWR 1.2:1 to 26.5 GHz **Model No: PE91051**	 1-24 $94.72 25-49 $89.98 50-99 $85.25 100+ $81.46 **SMA Female to MMCX Plug** **Model No: PE9475**	 1-24 $84.80 25-49 $80.56 50-99 $76.32 100+ $72.93 **SMA Female to MMCX Jack** **Model No: PE9477**	 1-9 $199.29 10-24 $189.33 25-49 $179.36 50+ $171.39 **SMA Female to Snap-On MMBX Plug** VSWR 1.08:1 to 12.4 GHz **Model No: PE91361**	 1-9 $179.88 10-24 $170.89 25-49 $161.89 50+ $154.70 **SMA Female to Snap-On MMBX Jack** VSWR 1.08:1 to 12.4 GHz **Model No: PE91363**
2	 1-24 $17.32 25-49 $16.45 50-99 $15.59 100+ $14.90 **SMA Female to N Male** VSWR 1.3:1 to 11 GHz **Model No: PE9081**	 1-9 $208.81 10-24 $198.37 25-49 $187.93 50+ $179.58 **SMA Female to QD N Male** **Model No: PE9684**	 1-24 $71.94 25-49 $68.34 50-99 $64.75 100+ $61.87 **SMA Female to N Male Bulkhead** Max. Freq. 11 GHz **Model No: PE9551**	 1-24 $96.86 25-49 $92.02 50-99 $87.17 100+ $83.30 **SMA Female to N Male 4 Hole Flange-Mounting Hole A05** VSWR 1.2:1 to 12.4 GHz **Model No: PE9275**	 PRECISION 1-9 $179.90 10-24 $170.91 25-49 $161.91 50+ $154.71 **SMA Female to N Male 4 Hole Flange-Mounting Hole A05** VSWR 1.15:1 to 18 GHz **Model No: PE9498**
3	 1-24 $21.11 25-49 $20.05 50-99 $19.00 100+ $18.15 **SMA Female to N Female** VSWR 1.3:1 to 11 GHz **Model No: PE9083**	 PRECISION 1-24 $102.32 25-49 $97.20 50-99 $92.09 100+ $88.00 **SMA Female to N Female** VSWR 1.15:1 to 18 GHz **Model No: PE9432**	 1-24 $25.45 25-49 $24.18 50-99 $22.91 100+ $21.89 **SMA Female to N Female Bulkhead** VSWR 1.3:1 to 11 GHz **Model No: PE9252**	 PRECISION 1-9 $159.88 10-24 $151.89 25-49 $143.89 50+ $137.50 **SMA Female to N Female Bulkhead** VSWR 1.15:1 to 18 GHz **Model No: PE9486**	 1-24 $65.60 25-49 $62.32 50-99 $59.04 100+ $56.42 **SMA Female to N Female 4 Hole Flange-Mounting Hole A05** VSWR 1.3:1 to 11 GHz **Model No: PE9104**
4	 PRECISION 1-9 $159.88 10-24 $151.89 25-49 $143.89 50+ $137.50 **SMA Female to N Female 4 Hole Flange-Mounting Hole A05** VSWR 1.15:1 to 18 GHz **Model No: PE9434**	 1-24 $76.52 25-49 $72.69 50-99 $68.87 100+ $65.81 **SMA Female to N Female Bulkhead** VSWR 1.25:1 to 6 GHz **Model No: PE9408**	 PRECISION 1-9 $164.13 10-24 $155.92 25-49 $147.72 50+ $141.15 **SMA Female to N Female Bulkhead-Mounting Hole G01** VSWR 1.15:1 to 18 GHz **Model No: PE9435**	 1-24 $65.10 25-49 $61.85 50-99 $58.59 100+ $55.99 **SMA Female to QMA Male** Max. Freq. 18 GHz **Model No: PE9786**	 1-24 $28.46 25-49 $27.04 50-99 $25.61 100+ $24.48 **SMA Female to SMB Plug** VSWR 1.3:1 to 4 GHz **Model No: PE9142**
5	 1-24 $59.06 25-49 $56.11 50-99 $53.15 100+ $50.79 **SMA Female to SMB Jack** VSWR 1.46:1 to 4 GHz **Model No: PE9143**	 1-24 $57.20 25-49 $54.34 50-99 $51.48 100+ $49.19 **SMA Female to SMC Plug** VSWR 1.2:1 to 10 GHz **Model No: PE9146**	 1-24 $61.70 25-49 $58.62 50-99 $55.53 100+ $53.06 **SMA Female to SMC Jack** Max. Freq. 10 GHz **Model No: PE9147**	 1-24 $72.93 25-49 $69.28 50-99 $65.64 100+ $62.72 **SMA Female to Full Detent SMP Male** VSWR 1.2:1 to 18 GHz **Model No: PE91305**	 1-24 $72.93 25-49 $69.28 50-99 $65.64 100+ $62.72 **SMA Female to Limited Detent SMP Male** VSWR 1.2:1 to 18 GHz **Model No: PE91306**
6	 1-24 $72.93 25-49 $69.28 50-99 $65.64 100+ $62.72 **SMA Female to Smooth Bore SMP Male** VSWR 1.2:1 to 18 GHz **Model No: PE91307**	 PRECISION 1-9 $133.81 10-24 $127.12 25-49 $120.43 50+ $115.08 **SMA Female to Smooth Bore SMP Male** VSWR 1.2:1 to 26.5 GHz **Model No: PE91049**	 PRECISION 1-9 $124.77 10-24 $118.53 25-49 $112.29 50+ $107.30 **SMA Female to Limited Detent SMP Male** VSWR 1.2:1 to 26.5 GHz **Model No: PE91050**	 PRECISION 1-9 $124.35 10-24 $118.13 25-49 $111.92 50+ $106.94 **SMA Female to Full Detent SMP Male** VSWR 1.2:1 to 26.5 GHz **Model No: PE91056**	 PRECISION 1-9 $182.19 10-24 $173.08 25-49 $163.97 50+ $156.68 **SMA Female to Limited Detent SMP Male** VSWR 1.2:1 to 18 GHz **Model No: PE9512**
7	 1-9 $414.68 10-24 $393.95 25-49 $373.21 50+ $356.62 **SMA Female to Limited Detent SMP Male** Max. Freq. 26.5 GHz **Model No: PE9778**	 1-9 $132.14 10-24 $125.53 25-49 $118.93 50+ $113.64 **SMA Female to Full Detent SMP Male Bulkhead-Mounting Hole F05** VSWR 1.3:1 to 26.5 GHz **Model No: PE91054**	 PRECISION 1-9 $126.30 10-24 $119.99 25-49 $113.67 50+ $108.62 **SMA Female to SMP Male 2 Hole Flange-Mounting Hole C05** VSWR 1.2:1 to 26.5 GHz **Model No: PE91057**	 PRECISION 1-9 $125.51 10-24 $119.23 25-49 $112.96 50+ $107.94 **SMA Female to Full Detent SMP Male 2 Hole Flange-Mounting Hole C01** VSWR 1.2:1 to 26.5 GHz **Model No: PE91058**	 PRECISION 1-9 $91.56 10-24 $86.98 25-49 $82.40 50+ $78.74 **SMA Female to Smooth Bore SMP Male 2 Hole Flange-Mounting Hole C05** VSWR 1.2:1 to 26.5 GHz **Model No: PE91061**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 PRECISION 1-9 $137.03 10-24 $130.18 25-49 $123.33 50+ $117.85 **SMA Female to Limited Detent SMP Male 2 Hole Flange-Mounting Hole C05** VSWR 1.2:1 to 26.5 GHz **Model No: PE91066**	 PRECISION 1-9 $146.82 10-24 $139.48 25-49 $132.14 50+ $126.27 **SMA Female to SMP Male 4 Hole Flange-Mounting Hole A01** VSWR 1.2:1 to 26.5 GHz **Model No: PE91059**	 1-24 $71.61 25-49 $68.03 50-99 $64.45 100+ $61.58 **SMA Female to SMP Female** VSWR 1.2:1 to 18 GHz **Model No: PE91308**	 PRECISION 1-9 $124.05 10-24 $117.85 25-49 $111.65 50+ $106.68 **SMA Female to SMP Female** VSWR 1.2:1 to 26.5 GHz **Model No: PE91064**	 PRECISION 1-9 $223.96 10-24 $212.76 25-49 $201.56 50+ $192.61 **SMA Female to SMP Female** VSWR 1.2:1 to 18 GHz **Model No: PE9779**
2	 1-24 $52.98 25-49 $50.33 50-99 $47.68 100+ $45.56 **SMA Female to SSMA Male** VSWR 1.3:1 to 18 GHz **Model No: PE9188**	 1-24 $72.54 25-49 $68.91 50-99 $65.29 100+ $62.38 **SMA Female to SSMA Female** VSWR 1.4:1 to 18 GHz **Model No: PE9399**	 1-24 $64.17 25-49 $60.96 50-99 $57.75 100+ $55.19 **SMA Female to SSMB Plug** **Model No: PE9402**	 1-24 $59.03 25-49 $56.08 50-99 $53.13 100+ $50.77 **SMA Female to SSMC Plug** VSWR 1.25:1 to 3 GHz **Model No: PE91380**	 1-24 $60.47 25-49 $57.45 50-99 $54.42 100+ $52.00 **SMA Female to SSMC Jack** VSWR 1.25:1 to 3 GHz **Model No: PE91433**
3	 1-24 $21.06 25-49 $20.01 50-99 $18.95 100+ $18.11 **SMA Female to TNC Male** VSWR 1.3:1 to 11 GHz **Model No: PE9077**	 1-9 $118.71 10-24 $112.77 25-49 $106.84 50+ $102.09 **SMA Female to TNC Male** VSWR 1.25:1 to 18 GHz **Model No: PE9440**	 1-24 $48.90 25-49 $46.46 50-99 $44.01 100+ $42.05 **SMA Female to TNC Female** Max. Freq. 11 GHz **Model No: PE9079**	 1-9 $153.09 10-24 $145.44 25-49 $137.78 50+ $131.66 **SMA Female to TNC Female** VSWR 1.25:1 to 18 GHz **Model No: PE9442**	 1-24 $51.75 25-49 $49.16 50-99 $46.58 100+ $44.51 **SMA Female to TNC Female Bulkhead-Mounting Hole B05** VSWR 1.3:1 to 11 GHz **Model No: PE9251**
4	 1-24 $54.04 25-49 $51.34 50-99 $48.64 100+ $46.47 **SMA Female to TNC Female 4 Hole Flange-Mounting Hole A03** **Model No: PE9276**	 1-24 $58.50 25-49 $55.58 50-99 $52.65 100+ $50.31 **SMA Female to UHF Male** VSWR 1.3:1 to 300 MHz **Model No: PE9415**	 1-24 $24.07 25-49 $22.87 50-99 $21.66 100+ $20.70 **SMA Female to UMCX Plug** VSWR 1.3:1 to 6 GHz **Model No: PE91005**	 1-24 $29.85 25-49 $28.36 50-99 $26.87 100+ $25.67 **SMA Female to UMCX Jack** VSWR 1.3:1 to 6 GHz **Model No: PE91006**	***Reverse Polarity SMA Between Series***
5	 1-24 $83.64 25-49 $79.46 50-99 $75.28 100+ $71.93 **SMA Male to Rev. Pol. MCX Plug** VSWR 1.2:1 to 6 GHz **Model No: PE9581**	 1-24 $59.26 25-49 $56.30 50-99 $53.33 100+ $50.96 **SMA Male to Rev. Pol. TNC Female** VSWR 1.25:1 to 11 GHz **Model No: PE9600**	 1-24 $56.97 25-49 $54.12 50-99 $51.27 100+ $48.99 **SMA Female to Rev. Pol. TNC Male** Max. Freq. 11 GHz **Model No: PE9602**	 1-24 $81.66 25-49 $77.58 50-99 $73.49 100+ $70.23 **SMA Female to Rev. Pol. TNC Female** VSWR 1.25:1 to 11 GHz **Model No: PE9603**	 1-24 $78.75 25-49 $74.81 50-99 $70.88 100+ $67.73 **Rev. Pol. SMA Male to N Female** VSWR 1.25:1 to 11 GHz **Model No: PE9732**
6	 1-24 $66.55 25-49 $63.22 50-99 $59.90 100+ $57.23 **Rev. Pol. SMA Male to TNC Male** VSWR 1.2:1 to 11 GHz **Model No: PE9597**	 1-24 $64.07 25-49 $60.87 50-99 $57.66 100+ $55.10 **Rev. Pol. SMA Male to TNC Female** VSWR 1.2:1 to 11 GHz **Model No: PE9596**	 1-24 $85.84 25-49 $81.55 50-99 $77.26 100+ $73.82 **Rev. Pol. SMA Female to N Male** VSWR 1.25:1 to 11 GHz **Model No: PE9733**	 1-24 $65.25 25-49 $61.99 50-99 $58.73 100+ $56.12 **Rev. Pol. SMA Female to TNC Male** VSWR 1.2:1 to 11 GHz **Model No: PE9598**	 1-24 $65.30 25-49 $62.04 50-99 $58.77 100+ $56.16 **Rev. Pol. SMA Female to TNC Female** VSWR 1.2:1 to 11 GHz **Model No: PE9599**
7	 1-24 $66.55 25-49 $63.22 50-99 $59.90 100+ $57.23 **Rev. Pol. SMA Male to Rev. Pol. TNC Male** VSWR 1.2:1 to 11 GHz **Model No: PE9605**	 1-24 $85.09 25-49 $80.84 50-99 $76.58 100+ $73.18 **Rev. Pol. SMA Male to Rev. Pol. TNC Female** VSWR 1.25:1 to 11 GHz **Model No: PE9604**	 1-24 $65.30 25-49 $62.04 50-99 $58.77 100+ $56.16 **Rev. Pol. SMA Female to Rev. Pol. TNC Male** VSWR 1.2:1 to 11 GHz **Model No: PE9607**	 1-24 $66.55 25-49 $63.22 50-99 $59.90 100+ $57.23 **Rev. Pol. SMA Female to Rev. Pol. TNC Female** VSWR 1.25:1 to 11 GHz **Model No: PE9606**	***SMB In-Series***

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	PRICE 1-24 $40.18; 25-49 $38.17; 50-99 $36.16; 100+ $34.55 **SMB Plug to SMB Plug** Max. Freq. 4 GHz **Model No:** PE9118	PRICE 1-24 $116.58; 25-49 $110.75; 50-99 $104.92; 100+ $100.26 **SMB Plug to SMB Plug Tee** Max. Freq. 4 GHz **Model No:** PE9310	PRICE 1-24 $64.06; 25-49 $60.86; 50-99 $57.65; 100+ $55.09 **SMB Plug to SMB Jack** VSWR 1.2:1 to 4 GHz **Model No:** PE9120	PRICE 1-24 $76.47; 25-49 $72.65; 50-99 $68.82; 100+ $65.76 **SMB Plug to SMB Jack Tee** **Model No:** PE9309	PRICE 1-24 $46.08; 25-49 $43.78; 50-99 $41.47; 100+ $39.63 **SMB Jack to SMB Plug Tee** Max. Freq. 100 MHz **Model No:** PE9243
2	PRICE 1-24 $54.71; 25-49 $51.97; 50-99 $49.24; 100+ $47.05 **SMB Jack to SMB Jack** VSWR 1.3:1 to 4 GHz **Model No:** PE9116	PRICE 1-24 $55.18; 25-49 $52.42; 50-99 $49.66; 100+ $47.45 **SMB Jack to SMB Jack Tee** **Model No:** PE9302	PRICE 1-24 $37.90; 25-49 $36.01; 50-99 $34.11; 100+ $32.59 **SMB Jack to SMB Jack Bulkhead-Mounting Hole B01** Max. Freq. 4 GHz **Model No:** PE9122	***SMB Between Series*** →	PRICE 1-24 $61.95; 25-49 $58.85; 50-99 $55.76; 100+ $53.28 **SMB Plug to BNC Male** Max. Freq. 4 GHz **Model No:** PE9135
3	PRICE 1-24 $65.28; 25-49 $62.02; 50-99 $58.75; 100+ $56.14 **SMB Plug to BNC Female** VSWR 1.3:1 to 4 GHz **Model No:** PE9137	PRICE 1-24 $54.97; 25-49 $52.22; 50-99 $49.47; 100+ $47.27 **SMB Plug to BNC Female Bulkhead-Mounting Hole B05** Max. Freq. 3 GHz **Model No:** PE9241	PRICE 1-24 $56.28; 25-49 $53.47; 50-99 $50.65; 100+ $48.40 **SMB Jack to BNC Male** Max. Freq. 4 GHz **Model No:** PE9132	PRICE 1-24 $64.11; 25-49 $60.90; 50-99 $57.70; 100+ $55.13 **SMB Jack to BNC Female** Max. Freq. 4 GHz **Model No:** PE9136	PRICE 1-24 $57.27; 25-49 $54.41; 50-99 $51.54; 100+ $49.25 **SMB Jack to BNC Female Bulkhead** VSWR 1.3:1 to 4 GHz **Model No:** PE9240
4	***SMC In-Series*** →	PRICE 1-24 $36.25; 25-49 $34.44; 50-99 $32.63; 100+ $31.18 **SMC Plug to SMC Plug** Max. Freq. 6 GHz **Model No:** PE9117	PRICE 1-24 $62.20; 25-49 $59.09; 50-99 $55.98; 100+ $53.49 **SMC Plug to SMC Plug Tee** **Model No:** PE9305	PRICE 1-24 $53.82; 25-49 $51.13; 50-99 $48.44; 100+ $46.29 **SMC Plug to SMC Jack** VSWR 1.2:1 to 10 GHz **Model No:** PE9119	PRICE 1-24 $68.41; 25-49 $64.99; 50-99 $61.57; 100+ $58.83 **SMC Plug to SMC Jack Right Angle** **Model No:** PE9303
5	PRICE 1-24 $49.05; 25-49 $46.60; 50-99 $44.15; 100+ $42.18 **SMC Jack to SMC Plug Tee** Max. Freq. 100 MHz **Model No:** PE9242	PRICE 1-24 $71.22; 25-49 $67.66; 50-99 $64.10; 100+ $61.25 **SMC Jack to SMC Jack Tee** **Model No:** PE9304	PRICE 1-24 $37.23; 25-49 $35.37; 50-99 $33.51; 100+ $32.02 **SMC Jack to SMC Jack Bulkhead-Mounting Hole B01** Max. Freq. 10 GHz **Model No:** PE91403	***SMC Between Series*** →	PRICE 1-24 $62.94; 25-49 $59.79; 50-99 $56.65; 100+ $54.13 **SMC Plug to BNC Male** **Model No:** PE9139
6	PRICE 1-24 $61.95; 25-49 $58.85; 50-99 $55.76; 100+ $53.28 **SMC Plug to BNC Female** VSWR 1.3:1 to 4 GHz **Model No:** PE9141	PRICE 1-24 $92.90; 25-49 $88.26; 50-99 $83.61; 100+ $79.89 **SMC Plug to SMB Plug** **Model No:** PE9281	PRICE 1-24 $47.31; 25-49 $44.94; 50-99 $42.58; 100+ $40.69 **SMC Plug to SMB Jack** **Model No:** PE9284	PRICE 1-24 $61.95; 25-49 $58.85; 50-99 $55.76; 100+ $53.28 **SMC Jack to BNC Male** **Model No:** PE9138	PRICE 1-24 $72.21; 25-49 $68.60; 50-99 $64.99; 100+ $62.10 **SMC Jack to BNC Female** VSWR 1.35:1 to 4 GHz **Model No:** PE9140
7	PRICE 1-24 $85.11; 25-49 $80.85; 50-99 $76.60; 100+ $73.19 **SMC Jack to BNC Female Bulkhead** **Model No:** PE9108	PRICE 1-24 $60.04; 25-49 $57.04; 50-99 $54.04; 100+ $51.63 **SMC Jack to SMB Plug** **Model No:** PE9282	PRICE 1-24 $61.62; 25-49 $58.54; 50-99 $55.46; 100+ $52.99 **SMC Jack to SMB Jack** **Model No:** PE9283	***SMP In-Series*** →	PRICE 1-24 $23.95; 25-49 $22.75; 50-99 $21.56; 100+ $20.60 **SMP Female to SMP Female** VSWR 1.2:1 to 12 GHz **Model No:** PE91102

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $81.24 25-49 $77.18 50-99 $73.12 100+ $69.87 **SMP Female to SMP Female** Max. Freq. 26.5 GHz **Model No: PE9776**	 PRICE 1-24 $24.47 25-49 $23.25 50-99 $22.02 100+ $21.04 **SMP Female to SMP Female** VSWR 1.2:1 to 8 GHz **Model No: PE91068**	 PRICE 1-24 $37.00 25-49 $35.15 50-99 $33.30 100+ $31.82 **SMP Female to SMP Female** Max. Freq. 40 GHz **Model No: PE91072**	 PRICE 1-24 $37.28 25-49 $35.42 50-99 $33.55 100+ $32.06 **SMP Female to SMP Female** Max. Freq. 40 GHz **Model No: PE91099**	 PRICE 1-24 $16.12 25-49 $15.31 50-99 $14.51 100+ $13.86 **SMP Female to SMP Female** VSWR 1.2:1 to 8 GHz **Model No: PE91101**
2	 PRICE 1-24 $74.97 25-49 $71.22 50-99 $67.47 100+ $64.47 **SMP Female to SMP Female** Max. Freq. 26.5 GHz **Model No: PE9775**	 PRICE 1-24 $48.36 25-49 $45.94 50-99 $43.52 100+ $41.59 **SMP Female to SMP Female** Max. Freq. 26.5 GHz **Model No: PE9777**	***SMP Between Series***	 PRICE 1-24 $14.12 25-49 $13.41 50-99 $12.71 100+ $12.14 **Push-On SMP Female to Snap-On MMBX Plug** VSWR 1.25:1 to 6 GHz **Model No: PE91364**	 PRICE 1-24 $30.24 25-49 $28.73 50-99 $27.22 100+ $26.01 **SMP Female to SMP Female** Max. Freq. 40 GHz **Model No: PE91065**
3	***SSMA In-Series***	 PRICE 1-9 $121.65 10-24 $115.57 25-49 $109.49 50+ $104.62 **SSMA Male to SSMA Male** **Model No: PE9357**	 PRICE 1-24 $78.35 25-49 $74.43 50-99 $70.52 100+ $67.38 **SSMA Male to SSMA Female** **Model No: PE9358**	 PRICE 1-9 $182.03 10-24 $172.93 25-49 $163.83 50+ $156.55 **QD SSMA Male to SSMA Female** **Model No: PE9685**	 PRICE 1-24 $97.00 25-49 $92.15 50-99 $87.30 100+ $83.42 **SSMA Male to SSMA Female Right Angle** VSWR 1.3:1 to 18 GHz **Model No: PE9334**
4	 PRICE 1-24 $69.17 25-49 $65.71 50-99 $62.25 100+ $59.49 **SSMA Female to SSMA Female** VSWR 1.3:1 to 25 GHz **Model No: PE9192**	 PRICE 1-24 $71.93 25-49 $68.33 50-99 $64.74 100+ $61.86 **SSMA Female to SSMA Female Bulkhead-Mounting Hole B01** **Model No: PE9189**	***SSMA Between Series***	 PRICE 1-9 $133.51 10-24 $126.83 25-49 $120.16 50+ $114.82 **SSMA Male to BNC Male** **Model No: PE9213**	 PRICE 1-24 $120.80 25-49 $114.76 50-99 $108.72 100+ $103.89 **SSMA Male to BNC Female** **Model No: PE91046**
5	 PRICE 1-24 $105.74 25-49 $100.45 50-99 $95.17 100+ $90.94 **SSMA Male to N Male** Max. Freq. 11 GHz **Model No: PE9351**	 PRICE 1-24 $105.81 25-49 $101.58 50-99 $98.40 100+ $96.29 **SSMA Female to BNC Male** **Model No: PE9191**	 PRICE 1-24 $94.29 25-49 $89.58 50-99 $84.86 100+ $81.09 **SSMA Female to N Male** **Model No: PE9352**	 PRICE 1-24 $86.91 25-49 $82.56 50-99 $78.22 100+ $74.74 **SSMA Female to N Female** **Model No: PE9354**	***SSMB Between Series***
6	 PRICE 1-24 $94.72 25-49 $89.98 50-99 $85.25 100+ $81.46 **SSMB Plug to BNC Male** **Model No: PE9393**	 PRICE 1-24 $116.94 25-49 $111.09 50-99 $105.25 100+ $100.57 **SSMB Plug to BNC Female** **Model No: PE9395**	 PRICE 1-24 $120.36 25-49 $114.34 50-99 $108.32 100+ $103.51 **SSMB Jack to BNC Male** **Model No: PE9392**	 PRICE 1-24 $120.32 25-49 $114.30 50-99 $108.29 100+ $103.48 **SSMB Jack to BNC Female** **Model No: PE9394**	***SSMC In-Series***
7	 PRICE 1-24 $57.39 25-49 $55.09 50-99 $53.37 100+ $52.22 **SSMC Plug to SSMC Plug** VSWR 1.25:1 to 12 GHz **Model No: PE91436**	 PRICE 1-24 $57.39 25-49 $54.52 50-99 $51.65 100+ $49.36 **SSMC Plug to SSMC Jack** VSWR 1.25:1 to 12 GHz **Model No: PE91434**	 PRICE 1-24 $57.39 25-49 $54.52 50-99 $51.65 100+ $49.36 **SSMC Jack to SSMC Jack Bulkhead** VSWR 1.25:1 to 4 GHz **Model No: PE91432**	***TNC In-Series***	 PRICE 1-24 $67.62 25-49 $64.24 50-99 $60.86 Low PIM 100+ $58.15 **TNC Male to TNC Male** VSWR 1.25:1 to 6 GHz **Model No: PE91172**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $58.24 25-49 $55.33 50-99 $52.42 100+ $50.09 **TNC Male to TNC Male** VSWR 1.2:1 to 6 GHz **Model No: PE91202**	 PRICE 1-24 $57.20 25-49 $54.34 50-99 $51.48 100+ $49.19 **TNC Male to TNC Male** VSWR 1.3:1 to 6 GHz **Model No: PE91239**	 PRICE 1-24 $38.32 25-49 $36.40 50-99 $34.49 100+ $32.96 **TNC Male to TNC Male** VSWR 1.3:1 to 1,000 MHz **Model No: PE9091**	 PRICE 1-9 $169.61 10-24 $161.13 25-49 $152.65 50+ $145.86 **TNC Male to TNC Male** VSWR 1.25:1 to 18 GHz **Model No: PE9445**	 PRICE 1-24 $102.38 25-49 $97.26 50-99 $92.14 100+ $88.05 **TNC Male to TNC Male Right Angle** **Model No: PE9560**
2	 PRICE 1-24 $58.24 25-49 $55.33 50-99 $52.42 100+ $50.09 **TNC Male to TNC Female** VSWR 1.2:1 to 6 GHz **Model No: PE91203**	 PRICE 1-24 $56.87 25-49 $54.03 50-99 $51.18 100+ $48.91 **TNC Male to TNC Female** VSWR 1.3:1 to 6 GHz **Model No: PE91240**	 PRICE 1-24 $78.69 25-49 $74.76 50-99 $70.82 PRECISION 100+ $67.67 **TNC Male to TNC Female** VSWR 1.15:1 to 18 GHz **Model No: PE91505**	 PRICE 1-24 $64.44 25-49 $61.22 50-99 $58.00 Low PIM 100+ $55.42 **TNC Male to TNC Female** VSWR 1.25:1 to 6 GHz **Model No: PE91173**	 PRICE 1-24 $27.14 25-49 $25.78 50-99 $24.43 100+ $23.34 **TNC Male to TNC Female** VSWR 1.5:1 to 11 GHz **Model No: PE9270**
3	 PRICE 1-24 $143.45 25-49 $133.41 50-99 $123.37 PRECISION 100+ $114.76 **TNC Male to TNC Female** VSWR 1.15:1 to 18 GHz **Model No: PE9443**	 PRICE 1-9 $203.71 10-24 $193.52 25-49 $183.34 50+ $175.19 **QD TNC Male to TNC Female** **Model No: PE9561**	 PRICE 1-24 $37.77 25-49 $35.88 50-99 $33.99 100+ $32.48 **TNC Male to TNC Female Right Angle** Max. Freq. 11 GHz **Model No: PE9100**	 PRICE 1-24 $94.71 25-49 $89.97 50-99 $85.24 100+ $81.45 **TNC Male to TNC Female Tee** **Model No: PE9290**	 PRICE 1-24 $31.46 25-49 $29.89 50-99 $28.31 100+ $27.06 **TNC Female to TNC Male Tee** Max. Freq. 11 GHz **Model No: PE9195**
4	 PRICE 1-24 $58.24 25-49 $55.33 50-99 $52.42 100+ $50.09 **TNC Female to TNC Female** VSWR 1.2:1 to 6 GHz **Model No: PE91204**	 PRICE 1-24 $52.11 25-49 $49.50 50-99 $46.90 100+ $44.81 **TNC Female to TNC Female** VSWR 1.3:1 to 6 GHz **Model No: PE91241**	 PRICE 1-24 $18.36 25-49 $17.44 50-99 $16.52 100+ $15.79 **TNC Female to TNC Female** VSWR 1.3:1 to 5 GHz **Model No: PE9099**	 PRICE 1-24 $59.06 25-49 $56.11 50-99 $53.15 Low PIM 100+ $50.79 **TNC Female to TNC Female** VSWR 1.25:1 to 6 GHz **Model No: PE91174**	 PRICE 1-9 $132.84 10-24 $126.20 25-49 $119.56 PRECISION 50+ $114.24 **TNC Female to TNC Female** VSWR 1.25:1 to 18 GHz **Model No: PE9444**
5	 PRICE 1-24 $36.36 25-49 $34.54 50-99 $32.72 100+ $31.27 **TNC Female to TNC Female Tee** **Model No: PE91381**	 PRICE 1-24 $48.34 25-49 $45.92 50-99 $43.51 NEW 100+ $41.57 **TNC Female to TNC Female Bulkhead** VSWR 1.35:1 to 12 GHz **Model No: PE91430**	 PRICE 1-24 $40.68 25-49 $38.65 50-99 $36.61 100+ $34.98 **TNC Female to TNC Female Bulkhead** VSWR 1.3:1 to 6 GHz **Model No: PE9154**	 PRICE 1-24 $57.80 25-49 $54.91 50-99 $52.02 100+ $49.71 **TNC Female to TNC Female Bulkhead** VSWR 1.2:1 to 6 GHz **Model No: PE91205**	 PRICE 1-24 $70.62 25-49 $67.09 50-99 $63.56 100+ $60.73 **TNC Female to TNC Female Bulkhead** VSWR 1.3:1 to 6 GHz **Model No: PE91242**
6	 PRICE 1-24 $34.09 25-49 $32.39 50-99 $30.68 100+ $29.32 **TNC Female to TNC Female Bulkhead** Max. Freq. 11 GHz **Model No: PE9287**	 PRICE 1-24 $35.93 25-49 $34.13 50-99 $32.34 100+ $30.90 **TNC Female to TNC Female 4 Hole Flange** VSWR 1.3:1 to 11 GHz **Model No: PE9288**	***Reverse Polarity TNC In-Series*** →	 PRICE 1-24 $48.73 25-49 $46.29 50-99 $43.86 100+ $41.91 **TNC Male to Rev. Pol. TNC Female** **Model No: PE9532**	 PRICE 1-24 $40.00 25-49 $38.00 50-99 $36.00 100+ $34.40 **TNC Female to Rev. Pol. TNC Male** VSWR 1.32:1 to 6 GHz **Model No: PE9531**
7	 PRICE 1-24 $37.53 25-49 $35.65 50-99 $33.78 100+ $32.28 **Rev. Pol. TNC Male to Rev. Pol. TNC Female Right Angle** VSWR 1.25:1 to 6 GHz **Model No: PE9918**	***TNC Between Series*** →	 PRICE 1-4 $757.61 5-9 $719.73 10-24 $681.85 PRECISION 25+ $651.54 **TNC Male to 7mm Sexless** VSWR 1.15:1 to 18 GHz **Model No: PE9219**	 PRICE 1-9 $274.38 10-24 $260.66 25-49 $246.94 50+ $235.97 **TNC Male to 7/16 DIN Female** VSWR 1.35:1 to 7.5 GHz **Model No: PE9638**	 PRICE 1-24 $33.38 25-49 $31.04 50-99 $28.71 NEW 100+ $26.70 **TNC Male to BNC Male** VSWR 1.4:1 to 4 GHz **Model No: PE91449**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $22.42 25-49 $21.30 50-99 $20.18 100+ $19.28 **TNC Male to BNC Female** VSWR 1.5:1 to 2 GHz **Model No: PE9088**	 PRICE 1-24 $74.10 25-49 $70.40 50-99 $66.69 100+ $63.73 **TNC Male to BNC Female Right Angle** **Model No: PE9783**	 PRICE 1-24 $125.37 25-49 $119.10 50-99 $112.83 100+ $107.82 **TNC Male to C Female** **Model No: PE9562**	 PRICE 1-24 $22.89 25-49 $21.75 50-99 $20.60 100+ $19.69 **TNC Male to FME Plug** **Model No: PE9699**	 PRICE 1-24 $13.65 25-49 $12.97 50-99 $12.29 100+ $11.74 **TNC Male to FME Plug Right Angle** **Model No: PE9700**
2	 PRICE 1-24 $20.08 25-49 $19.08 50-99 $18.07 100+ $17.27 **TNC Male to FME Jack** **Model No: PE9713**	 PRICE 1-24 $96.31 25-49 $91.49 50-99 $86.68 100+ $82.83 **TNC Male to HN Male** **Model No: PE9563**	 PRICE 1-24 $77.10 25-49 $73.25 50-99 $69.39 100+ $66.31 **TNC Male to MCX Plug** **Model No: PE9543**	 PRICE 1-24 $85.34 25-49 $81.07 50-99 $76.81 100+ $73.39 **TNC Male to MCX Jack** **Model No: PE9542**	 PRICE 1-24 $25.12 25-49 $23.86 50-99 $22.61 100+ $21.60 **TNC Male to Mini UHF Female** **Model No: PE9345**
3	 PRICE 1-24 $71.43 25-49 $67.86 50-99 $64.29 100+ $61.43 **TNC Male to SMC Jack** **Model No: PE9226**	 PRICE 1-24 $30.51 25-49 $28.98 50-99 $27.46 100+ $26.24 **TNC Male to UHF Female** Max. Freq. 300 MHz **Model No: PE9291**	 PRECISION PRICE 1-9 $616.14 10-24 $585.33 25-49 $554.53 50+ $529.88 **TNC Female to 7mm Sexless** VSWR 1.15:1 to 18 GHz **Model No: PE9218**	 PRICE 1-9 $290.86 10-24 $276.32 25-49 $261.77 50+ $250.14 **TNC Female to 7/16 DIN Female** Max. Freq. 7.5 GHz **Model No: PE91392**	 PRICE 1-24 $32.18 25-49 $30.57 50-99 $28.96 100+ $27.67 **TNC Female to BNC Male** VSWR 1.3:1 to 4 GHz **Model No: PE9098**
4	 PRICE 1-24 $43.04 25-49 $40.89 50-99 $38.74 100+ $37.01 **TNC Female to BNC Female** VSWR 1.3:1 to 4 GHz **Model No: PE9097**	 PRICE 1-9 $145.85 10-24 $138.56 25-49 $131.27 50+ $125.43 **TNC Female to C Male** Max. Freq. 11 GHz **Model No: PE9564**	 PRICE 1-24 $6.21 25-49 $5.90 50-99 $5.59 100+ $5.34 **TNC Female to FME Jack** **Model No: PE9714**	 PRICE 1-24 $84.09 25-49 $79.89 50-99 $75.68 100+ $72.32 **TNC Female to MCX Plug** **Model No: PE9545**	 PRICE 1-24 $88.98 25-49 $84.53 50-99 $80.08 100+ $76.52 **TNC Female to MCX Jack** **Model No: PE9544**
5	 PRICE 1-24 $103.19 25-49 $98.03 50-99 $92.87 100+ $88.74 **TNC Female to MCX Jack Bulkhead-Mounting Hole B04** **Model No: PE9521**	 PRICE 1-24 $22.79 25-49 $21.65 50-99 $20.51 100+ $19.60 **TNC Female to Mini UHF Male** Max. Freq. 2.5 GHz **Model No: PE9346**	 PRICE 1-9 $229.36 10-24 $217.89 25-49 $206.42 50+ $197.25 **TNC Female to Limited Detent SMP Male Bulkhead** VSWR 1.3:1 to 8 GHz **Model No: PE91073**	 PRICE 1-24 $39.94 25-49 $37.94 50-99 $35.95 100+ $34.35 **TNC Female to UHF Male** VSWR 1.3:1 to 300 MHz **Model No: PE9372**	***Reverse Polarity TNC Between Series***
6	 PRICE 1-24 $39.47 25-49 $37.50 50-99 $35.52 100+ $33.94 **Rev. Pol. TNC Female to BNC Male** Max. Freq. 4 GHz **Model No: PE91087**	***UHF In-Series***	 PRICE 1-24 $22.85 25-49 $21.71 50-99 $20.57 100+ $19.65 **UHF Male to UHF Male** VSWR 1.3:1 to 300 MHz **Model No: PE91487**	 PRICE 1-24 $34.30 25-49 $32.59 50-99 $30.87 100+ $29.50 **UHF Male to UHF Female Right Angle** Max. Freq. 300 MHz **Model No: PE9209**	 PRICE 1-24 $28.57 25-49 $27.14 50-99 $25.71 100+ $24.57 **UHF Female to UHF Male Tee** **Model No: PE9095**
7	 PRICE 1-24 $20.72 25-49 $19.68 50-99 $18.65 100+ $17.82 **UHF Female to UHF Female** VSWR 1.3:1 to 300 MHz **Model No: PE9094**	 PRICE 1-24 $52.55 25-49 $49.92 50-99 $47.30 100+ $45.19 **UHF Female to UHF Female Bulkhead-Mounting Hole F03** Max. Freq. 300 MHz **Model No: PE9114**	***UHF Between Series***	 PRICE 1-24 $30.95 25-49 $29.40 50-99 $27.86 100+ $26.62 **UHF Male to BNC Male** **Model No: PE9201**	 PRICE 1-24 $15.61 25-49 $14.83 50-99 $14.05 100+ $13.42 **UHF Male to BNC Female** VSWR 1.3:1 to 300 MHz **Model No: PE91328**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $40.55 25-49 $38.52 50-99 $36.50 100+ $34.87 **UHF Male to 75 Ohm F Female** **Model No:** PE9165	 PRICE 1-24 $22.21 25-49 $21.10 50-99 $19.99 100+ $19.10 **UHF Male to FME Plug** **Model No:** PE9701	 PRICE 1-24 $23.21 25-49 $22.05 50-99 $20.89 100+ $19.96 **UHF Male to Mini UHF Female** **Model No:** PE9348	 PRICE 1-24 $18.91 25-49 $17.96 50-99 $17.02 100+ $16.26 **UHF Female to BNC Male** VSWR 1.3:1 to 300 MHz **Model No:** PE91329	 PRICE 1-24 $28.57 25-49 $27.14 50-99 $25.71 100+ $24.57 **UHF Female to BNC Female** **Model No:** PE9421
2	 PRICE 1-24 $36.65 25-49 $34.82 50-99 $32.99 100+ $31.52 **UHF Female to 75 Ohm F Female** **Model No:** PE9167	 PRICE 1-24 $17.11 25-49 $16.25 50-99 $15.40 100+ $14.71 **UHF Female to Mini UHF Male** VSWR 1.3:1 to 300 MHz **Model No:** PE91447	***75 Ohm BNC In-Series*** →	 PRICE 1-24 $31.42 25-49 $29.85 50-99 $28.28 100+ $27.02 **75 Ohm BNC Male to 75 Ohm BNC Male** VSWR 1.5:1 to 300 MHz **Model No:** PE9364	 PRICE 1-24 $44.73 25-49 $42.49 50-99 $40.26 100+ $38.47 **75 Ohm BNC Male to 75 Ohm BNC Female Right Angle** Max. Freq. 4 GHz **Model No:** PE9361
3	 PRICE 1-24 $54.48 25-49 $51.76 50-99 $49.03 100+ $46.85 **75 Ohm BNC Female to 75 Ohm BNC Male Tee** Max. Freq. 100 MHz **Model No:** PE9365	 PRICE 1-24 $31.54 25-49 $29.96 50-99 $28.39 100+ $27.12 **75 Ohm BNC Female to 75 Ohm BNC Female** VSWR 1.3:1 to 1,000 MHz **Model No:** PE9362	 PRICE 1-24 $43.64 25-49 $41.46 50-99 $39.28 100+ $37.53 **75 Ohm BNC Female to 75 Ohm BNC Female Bulkhead** VSWR 1.3:1 to 1,000 MHz **Model No:** PE9363	 PRICE 1-24 $47.99 25-49 $45.59 50-99 $43.19 100+ $41.27 **75 Ohm BNC Female to 75 Ohm BNC Female 4 Hole Flange-Mounting Hole A03** Max. Freq. 1,000 MHz **Model No:** PE9367	 NEW PRICE 1-24 $13.28 25-49 $12.62 50-99 $11.95 100+ $11.42 **75 Ohm BNC Female to 75 Ohm BNC Female Bulkhead** VSWR 1.5:1 to 500 MHz **Model No:** PE9791
4	***75 Ohm BNC Between Series*** →	 PRICE 1-24 $27.58 25-49 $26.20 50-99 $24.82 100+ $23.72 **75 Ohm BNC Female to 75 Ohm F Female Bulkhead** VSWR 1.3:1 to 1,000 MHz **Model No:** PE91324	***75 Ohm F In-Series*** →	 PRECISION PRICE 1-24 $45.23 25-49 $42.97 50-99 $40.71 100+ $38.90 **75 Ohm F Male to 75 Ohm F Male** VSWR 1.17:1 to 3 GHz **Model No:** PE91348	 PRICE 1-24 $112.48 25-49 $106.86 50-99 $101.23 100+ $96.73 **75 Ohm F Male to 75 Ohm F Male** VSWR 1.3:1 to 3 GHz **Model No:** PE9760
5	 PRICE 1-24 $10.55 25-49 $10.02 50-99 $9.50 100+ $9.07 **75 Ohm Push-On F Male to 75 Ohm F Female** VSVR 1.5:1 to 1,000 MHz **Model No:** PE9160	 PRICE 1-24 $110.82 25-49 $105.28 50-99 $99.74 100+ $95.31 **75 Ohm F Male to 75 Ohm F Female** VSVR 1.3:1 to 3 GHz **Model No:** PE9759	 PRICE 1-24 $12.29 25-49 $11.68 50-99 $11.06 100+ $10.57 **75 Ohm F Male to 75 Ohm F Female Right Angle** Max. Freq. 1,000 MHz **Model No:** PE9166	 PRECISION PRICE 1-24 $28.26 25-49 $26.85 50-99 $25.43 100+ $24.30 **75 Ohm F Female to 75 Ohm F Female** VSVR 1.28:1 to 3 GHz **Model No:** PE91349	 PRICE 1-24 $3.27 25-49 $3.11 50-99 $2.94 100+ $2.81 **75 Ohm F Female to 75 Ohm F Female** VSVR 1.35:1 to 500 MHz **Model No:** PE9164
6	 PRICE 1-24 $9.76 25-49 $9.27 50-99 $8.78 100+ $8.39 **75 Ohm F Female to 75 Ohm F Female Bulkhead-Mounting Hole B04** VSVR 1.3:1 to 250 MHz **Model No:** PE9734	***75 Ohm F Between Series*** →	 PRICE 1-9 $138.58 10-24 $131.65 25-49 $124.72 50+ $119.18 **75 Ohm F Male to 75 Ohm BNC Male** VSVR 1.3:1 to 3 GHz **Model No:** PE9742	 PRICE 1-9 $147.44 10-24 $140.07 25-49 $132.70 50+ $126.80 **75 Ohm F Male to 75 Ohm BNC Female** VSVR 1.3:1 to 3 GHz **Model No:** PE9743	 PRICE 1-24 $21.12 25-49 $20.06 50-99 $19.01 100+ $18.16 **75 Ohm F Male to 75 Ohm PAL Plug** **Model No:** PE9633
7	 PRICE 1-24 $21.12 25-49 $20.06 50-99 $19.01 100+ $18.16 **75 Ohm F Male to 75 Ohm PAL Jack** **Model No:** PE9632	 PRICE 1-9 $156.39 10-24 $148.57 25-49 $140.75 50+ $134.50 **75 Ohm F Female to 75 Ohm BNC Male** VSVR 1.3:1 to 3 GHz **Model No:** PE9741	 PRICE 1-9 $163.22 10-24 $155.06 25-49 $146.90 50+ $140.37 **75 Ohm F Female to 75 Ohm BNC Female** VSVR 1.3:1 to 3 GHz **Model No:** PE9744	 PRICE 1-24 $21.12 25-49 $20.06 50-99 $19.01 100+ $18.16 **75 Ohm F Female to 75 Ohm PAL Jack** **Model No:** PE9634	 PRICE 1-24 $20.44 25-49 $19.42 50-99 $18.40 100+ $17.58 **75 Ohm F Female to 75 Ohm RCA Plug** **Model No:** PE9163

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	**75 Ohm Mini SMB In-Series** →	PRICE: 1-24 $41.25; 25-49 $39.19; 50-99 $37.13; 100+ $35.48 **75 Ohm Mini SMB Plug to 75 Ohm Mini SMB Plug** Model No: PE9609	PRICE: 1-24 $58.64; 25-49 $55.71; 50-99 $52.78; 100+ $50.43 **75 Ohm Mini SMB Plug to 75 Ohm Mini SMB Jack** Model No: PE9610	PRICE: 1-24 $41.25; 25-49 $39.19; 50-99 $37.13; 100+ $35.48 **75 Ohm Mini SMB Jack to 75 Ohm Mini SMB Jack** Model No: PE9608	PRICE: 1-24 $53.26; 25-49 $50.60; 50-99 $47.93; 100+ $45.80 **75 Ohm Mini SMB Jack to 75 Ohm Mini SMB Jack Bulkhead** Model No: PE9611
2	**75 Ohm Mini SMB Between Series** →	PRICE: 1-24 $84.84; 25-49 $80.60; 50-99 $76.36; 100+ $72.96 **75 Ohm Mini SMB Plug to 75 Ohm BNC Male** Model No: PE9616	PRICE: 1-24 $70.62; 25-49 $67.09; 50-99 $63.56; 100+ $60.73 **75 Ohm Mini SMB Plug to 75 Ohm BNC Female** Model No: PE9617	PRICE: 1-24 $90.06; 25-49 $85.56; 50-99 $81.05; 100+ $77.45 **75 Ohm Mini SMB Jack to 75 Ohm BNC Male** Model No: PE9618	PRICE: 1-24 $100.51; 25-49 $95.48; 50-99 $90.46; 100+ $86.44 **75 Ohm Mini SMB Jack to 75 Ohm BNC Female** Model No: PE9619
3	**75 Ohm N In-Series** →	PRICE: 1-24 $41.41; 25-49 $39.34; 50-99 $37.27; 100+ $35.61 **75 Ohm N Male to 75 Ohm N Male** Max. Freq. 1.5 GHz Model No: PE9308	PRICE: 1-24 $45.00; 25-49 $42.75; 50-99 $40.50; 100+ $38.70 **75 Ohm N Male to 75 Ohm N Female** Max. Freq. 1.5 GHz Model No: PE9391	PRICE: 1-24 $52.64; 25-49 $50.01; 50-99 $47.38; 100+ $45.27 **75 Ohm N Male to 75 Ohm N Female Right Angle** Max. Freq. 1.5 GHz Model No: PE9307	PRICE: 1-24 $39.62; 25-49 $37.64; 50-99 $35.66; 100+ $34.07 **75 Ohm N Female to 75 Ohm N Female** VSWR 1.3:1 to 1,000 MHz Model No: PE9306
4	PRICE: 1-24 $123.30; 25-49 $117.14; 50-99 $110.97; 100+ $106.04 **75 Ohm N Female to 75 Ohm N Female Bulkhead-Mounting Hole G01** Model No: PE9417	PRICE: 1-24 $65.96; 25-49 $62.66; 50-99 $59.36; 100+ $56.73 **75 Ohm N Female to 75 Ohm N Female Bulkhead** VSWR 1.35:1 to 1.5 GHz Model No: PE9416	**75 Ohm N Between Series** →	PRICE: 1-24 $77.67; 25-49 $73.79; 50-99 $69.90; 100+ $66.80 **75 Ohm N Male to 75 Ohm BNC Male** Max. Freq. 1,000 MHz Model No: PE9370	PRICE: 1-24 $37.13; 25-49 $35.27; 50-99 $33.42; 100+ $31.93 **75 Ohm N Male to 75 Ohm BNC Female** VSWR 1.3:1 to 1,000 MHz Model No: PE9369
5	PRICE: 1-9 $201.12; 10-24 $191.06; 25-49 $181.01; 50+ $172.96 **75 Ohm N Male to 75 Ohm F Male** VSWR 1.3:1 to 3 GHz Model No: PE9738	PRICE: 1-24 $51.43; 25-49 $48.86; 50-99 $46.29; 100+ $44.23 **75 Ohm N Male to 75 Ohm F Female** Max. Freq. 1,000 MHz Model No: PE9396	PRICE: 1-24 $109.74; 25-49 $104.25; 50-99 $98.77; 100+ $94.38 **75 Ohm N Male to 75 Ohm Mini SMB Plug** Model No: PE9612	PRICE: 1-24 $94.34; 25-49 $89.62; 50-99 $84.91; 100+ $81.13 **75 Ohm N Male to 75 Ohm Mini SMB Jack** Model No: PE9614	PRICE: 1-24 $119.65; 25-49 $113.67; 50-99 $107.69; 100+ $102.90 **75 Ohm N Male to 75 Ohm SMB Plug** Model No: PE9584
6	PRICE: 1-24 $96.07; 25-49 $91.27; 50-99 $86.46; 100+ $82.62 **75 Ohm N Male to 75 Ohm SMB Jack** Model No: PE9582	PRICE: 1-24 $97.57; 25-49 $92.69; 50-99 $87.81; 100+ $83.91 **75 Ohm N Male to 75 Ohm SMC Jack** Model No: PE9586	PRICE: 1-24 $83.78; 25-49 $79.59; 50-99 $75.40; 100+ $72.05 **75 Ohm N Male to 75 Ohm TNC Male** Max. Freq. 500 MHz Model No: PE9626	PRICE: 1-24 $58.64; 25-49 $55.71; 50-99 $52.78; 100+ $50.43 **75 Ohm N Male to 75 Ohm TNC Female** Max. Freq. 500 MHz Model No: PE9627	PRICE: 1-24 $41.41; 25-49 $39.34; 50-99 $37.27; 100+ $35.61 **75 Ohm N Female to 75 Ohm BNC Male** Max. Freq. 1,000 MHz Model No: PE9368
7	PRICE: 1-24 $54.12; 25-49 $51.41; 50-99 $48.71; 100+ $46.54 **75 Ohm N Female to 75 Ohm BNC Female** Max. Freq. 1,000 MHz Model No: PE9371	PRICE: 1-24 $52.94; 25-49 $50.29; 50-99 $47.65; 100+ $45.53 **75 Ohm N Female to 75 Ohm F Male** VSWR 1.3:1 to 3 GHz Model No: PE9397	PRICE: 1-24 $117.50; 25-49 $111.63; 50-99 $105.75; 100+ $101.05 **75 Ohm N Female to 75 Ohm F Male** VSWR 1.3:1 to 3 GHz Model No: PE9739	PRICE: 1-9 $166.77; 10-24 $158.43; 25-49 $150.09; 50+ $143.42 **75 Ohm N Female to 75 Ohm F Female** VSWR 1.3:1 to 3 GHz Model No: PE9740	PRICE: 1-9 $124.76; 10-24 $118.52; 25-49 $112.28; 50+ $107.29 **75 Ohm N Female to 75 Ohm Mini SMB Plug** Model No: PE9613

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $98.11 25-49 $93.20 50-99 $88.30 100+ $84.37 **75 Ohm N Female to 75 Ohm Mini SMB Jack** Max. Freq. 1,000 MHz **Model No: PE9615**	 PRICE 1-24 $129.35 25-49 $122.88 50-99 $116.42 100+ $111.24 **75 Ohm N Female to 75 Ohm SMB Plug** **Model No: PE9585**	 PRICE 1-24 $111.20 25-49 $105.64 50-99 $100.08 100+ $95.63 **75 Ohm N Female to 75 Ohm SMB Jack** **Model No: PE9583**	 PRICE 1-24 $104.84 25-49 $99.60 50-99 $94.36 100+ $90.16 **75 Ohm N Female to 75 Ohm SMC Plug** **Model No: PE9589**	 PRICE 1-24 $104.41 25-49 $99.19 50-99 $93.97 100+ $89.79 **75 Ohm N Female to 75 Ohm SMC Jack** **Model No: PE9587**
2	 PRICE 1-24 $58.64 25-49 $55.71 50-99 $52.78 100+ $50.43 **75 Ohm N Female to 75 Ohm TNC Male** Max. Freq. 500 MHz **Model No: PE9628**	 PRICE 1-24 $58.64 25-49 $55.71 50-99 $52.78 100+ $50.43 **75 Ohm N Female to 75 Ohm TNC Female** Max. Freq. 1,000 MHz **Model No: PE9629**	***75 Ohm PAL In-Series***	 PRICE 1-24 $13.62 25-49 $12.94 50-99 $12.26 100+ $11.71 **75 Ohm PAL Plug to 75 Ohm PAL Plug** **Model No: PE9680**	***75 Ohm SMB In-Series***
3	 PRICE 1-24 $67.34 25-49 $63.97 50-99 $60.61 100+ $57.91 **75 Ohm SMB Plug to 75 Ohm SMB Plug** **Model No: PE9271**	 PRICE 1-24 $73.06 25-49 $69.41 50-99 $65.75 100+ $62.83 **75 Ohm SMB Jack to 75 Ohm SMB Plug Tee** **Model No: PE9245**	 PRICE 1-24 $73.53 25-49 $69.85 50-99 $66.18 100+ $63.24 **75 Ohm SMB Jack to 75 Ohm SMB Jack** Max. Freq. 4 GHz **Model No: PE9248**	***75 Ohm SMB Between Series***	 PRICE 1-24 $72.71 25-49 $69.07 50-99 $65.44 100+ $62.53 **75 Ohm SMB Plug to BNC Female** **Model No: PE9232**
4	 PRICE 1-24 $69.90 25-49 $66.41 50-99 $62.91 100+ $60.11 **75 Ohm SMB Plug to 75 Ohm Mini SMB Jack** Max. Freq. 2 GHz **Model No: PE9736**	 PRICE 1-24 $68.68 25-49 $65.25 50-99 $61.81 100+ $59.06 **75 Ohm SMB Jack to BNC Male** **Model No: PE9229**	 PRICE 1-24 $78.35 25-49 $74.43 50-99 $70.52 100+ $67.38 **75 Ohm SMB Jack to 75 Ohm Mini SMB Plug** **Model No: PE9735**	***75 Ohm SMC In-Series***	 PRICE 1-24 $62.18 25-49 $59.07 50-99 $55.96 100+ $53.47 **75 Ohm SMC Jack to 75 Ohm SMC Plug Tee** **Model No: PE9244**
5	 PRICE 1-24 $47.23 25-49 $44.87 50-99 $42.51 100+ $40.62 **75 Ohm SMC Jack to 75 Ohm SMC Jack** **Model No: PE9227**	 PRICE 1-24 $62.05 25-49 $58.95 50-99 $55.85 100+ $53.36 **75 Ohm SMC Jack to 75 Ohm SMC Jack Bulkhead-Mounting Hole B03** **Model No: PE9228**	***75 Ohm SMC Between Series***	 PRICE 1-24 $68.58 25-49 $65.15 50-99 $61.72 100+ $58.98 **75 Ohm SMC Jack to BNC Female** **Model No: PE9235**	***75 Ohm TNC In-Series***
6	 PRICE 1-24 $105.72 25-49 $100.43 50-99 $95.15 100+ $90.92 **75 Ohm TNC Male to 75 Ohm TNC Female Right Angle** **Model No: PE9623**	 PRICE 1-24 $42.42 25-49 $40.30 50-99 $38.18 100+ $36.48 **75 Ohm TNC Female to 75 Ohm TNC Female** Max. Freq. 1,000 MHz **Model No: PE9622**	 PRICE 1-24 $58.64 25-49 $55.71 50-99 $52.78 100+ $50.43 **75 Ohm TNC Female to 75 Ohm TNC Female Bulkhead-Mounting Hole B06** Max. Freq. 1,000 MHz **Model No: PE9625**	 PRICE 1-24 $100.05 25-49 $95.05 50-99 $90.05 100+ $86.04 **75 Ohm TNC Female to 75 Ohm TNC Female Bulkhead** **Model No: PE9624**	***75 Ohm TNC Between Series***
7	 PRICE 1-24 $31.83 25-49 $30.24 50-99 $28.65 100+ $27.37 **75 Ohm TNC Male to 75 Ohm BNC Female** Max. Freq. 500 MHz **Model No: PE9631**	 PRICE 1-24 $88.72 25-49 $84.28 50-99 $79.85 100+ $76.30 **75 Ohm TNC Male to 75 Ohm F Male** VSWR 1.35:1 to 2 GHz **Model No: PE91081**	 PRICE 1-24 $78.88 25-49 $74.94 50-99 $70.99 100+ $67.84 **75 Ohm TNC Male to 75 Ohm F Female** VSWR 1.35:1 to 2 GHz **Model No: PE91080**	 PRICE 1-24 $58.64 25-49 $55.71 50-99 $52.78 100+ $50.43 **75 Ohm TNC Female to 75 Ohm BNC Male** Max. Freq. 1,000 MHz **Model No: PE9630**	 PRICE 1-24 $104.17 25-49 $98.96 50-99 $93.75 100+ $89.59 **75 Ohm TNC Female to 75 Ohm F Male** VSWR 1.35:1 to 2 GHz **Model No: PE91083**

See Our Website For Current Pricing & Real-Time Stock Availability!

ADAPTERS

See Adapter Locator on Pages 10-15
See Page 409 for Mounting Holes

	A	B	C	D	E
1	 PRICE 1-24 $88.73 25-49 $85.18 50-99 $82.52 100+ $80.74 **75 Ohm TNC Female to 75 Ohm F Female** VSWR 1.35:1 to 2 GHz **Model No: PE91082**	***BNC Twinax In-Series*** →	 PRICE 1-24 $94.04 25-49 $89.34 50-99 $84.64 100+ $80.87 **78 Ohm BNC Twinax Plug to 78 Ohm BNC Twinax Plug** **Model No: PE9376**	 PRICE 1-24 $93.42 25-49 $88.75 50-99 $84.08 100+ $80.34 **78 Ohm BNC Twinax Plug to 78 Ohm BNC Twinax Jack Right Angle** **Model No: PE9377**	 PRICE 1-24 $92.99 25-49 $88.34 50-99 $83.69 100+ $79.97 **78 Ohm BNC Twinax Jack to 78 Ohm BNC Twinax Plug Tee** **Model No: PE9375**
2	 PRICE 1-24 $42.14 25-49 $40.03 50-99 $37.93 100+ $36.24 **78 Ohm BNC Twinax Jack to 78 Ohm BNC Twinax Jack** Max. Freq. 500 MHz **Model No: PE9378**	 PRICE 1-24 $58.75 25-49 $55.81 50-99 $52.88 100+ $50.53 **78 Ohm BNC Twinax Jack to 78 Ohm BNC Twinax Jack Bulkhead** Max. Freq. 500 MHz **Model No: PE9280**	***3/4"-20 Twinax In-Series*** →	 PRICE 1-24 $44.69 25-49 $42.46 50-99 $40.22 100+ $38.43 **95 Ohm 3/4"-20 Twinax Female to 95 Ohm 3/4"-20 Twinax Male Tee** Max. Freq. 400 MHz **Model No: PE9374**	 PRICE 1-24 $33.56 25-49 $31.88 50-99 $30.20 100+ $28.86 **95 Ohm 3/4"-20 Twinax Female to 95 Ohm 3/4"-20 Twinax Female** **Model No: PE9199**
3	 PRICE 1-24 $57.44 25-49 $54.57 50-99 $51.70 100+ $49.40 **95 Ohm 3/4"-20 Twinax Female to 95 Ohm 3/4"-20 Twinax Female Bulkhead** **Model No: PE9373**	***Banana Between Series*** →	 PRICE 1-24 $52.92 25-49 $50.27 50-99 $47.63 100+ $45.51 **Banana Plug to BNC Female** **Model No: PE9175**	***Double Banana Between Series*** →	 PRICE 1-24 $27.33 25-49 $25.96 50-99 $24.60 NEW 100+ $23.50 **Double Banana Plug to BNC Male** **Model No: PE9009**
4	 PRICE 1-24 $27.57 25-49 $26.19 50-99 $24.81 NEW 100+ $23.71 **Double Banana Plug to BNC Female** **Model No: PE9008**	***Banana Binding Post Between Series*** →	 PRICE 1-24 $21.53 25-49 $20.45 50-99 $19.38 NEW 100+ $18.52 **Banana Binding Post Jack to BNC Male** **Model No: PE9169**	***Double Banana Binding Post Between Series*** →	 PRICE 1-24 $31.41 25-49 $29.84 50-99 $28.27 NEW 100+ $27.01 **Double Banana Binding Post Jack to BNC Female** **Model No: PE9013**
5	***Non Constant Ohm BNC Triax In-Series*** →	 PRICE 1-9 $165.76 10-24 $157.47 25-49 $149.18 50+ $142.55 **BNC Triax Male to BNC Triax Female Tee** Max. Freq. 500 MHz **Model No: PE91106**	 PRICE 1-24 $46.85 25-49 $44.51 50-99 $42.17 100+ $40.29 **BNC Triax Female to BNC Triax Female** Max. Freq. 500 MHz **Model No: PE91107**	 PRICE 1-9 $159.50 10-24 $151.53 25-49 $143.55 50+ $137.17 **BNC Triax Female to BNC Triax Female Bulkhead-Mounting Hole B15** Max. Freq. 500 MHz **Model No: PE91105**	***Visit pasternack.com for our complete offering of adapters***

See Our Website For Current Pricing & Real-Time Stock Availability!

Amplifiers Selection Guide

3 Easy Ways to Find your Product.....

1. Search by PE Part Number

If you know the PE part number you are searching for, please reference our Part Number Index on Page 395.

2. Quick Reference Guide

Bi Directional Amplifiers 51
Broadband Amplifiers 51
USB Controlled 52
Bench Top 52
DC Coupled Amplifiers 53
Gain Block Amplifiers 53
Limiting Amplifiers 53
Log Amplifiers 54
Low Noise Amplifiers 54
Standard 54
Input Protected 55
Power Amplifiers 55
Power Amplifiers (<4W) 55
High Power Amplifiers (>4W) 57
GaN High Power Amplifiers 58
Variable Amplifiers 59
Amplifier Accessories 59

3. Amplifiers Locator

Frequency	Model No.	Page	C/R
DC to:			
1.5 GHz	PE15A86001	53	31
17 MHz	PE15A86002	53	30
2 GHz	PE15A86000	53	32
0.009 MHz to:			
3 GHz	PE15A1007	54	41
0.01 MHz to:			
1.4 GHz	PE15A1055	54	43
2 GHz	PE15A1059	54	44
3 GHz	PE15A3308	52	57
500 MHz	PE15A1046	54	42
0.03 MHz to:			
600 MHz	PE15A1047	54	45
0.1 MHz to:			
10 GHz	PE15A3311	52	58
0.15 MHz to:			
230 MHz	PE15A5028	57	94
	PE15A5028F	57	95
0.3 MHz to:			
6.5 GHz	PE15A3310	52	59
0.5 MHz to:			
500 MHz	PE15A5029	57	96
	PE15A5029F	57	97
1 MHz to:			
1 GHz	PE15A5030	55	20
	PE15A5030F	55	21
3 GHz	PE15A3309	52	60
500 MHz	PE15A1045	54	46
1.5 MHz to:			
100 MHz	PE15A5056	55	23
30 MHz	PE15A5055	55	22

Frequency	Model No.	Page	C/R
10 MHz to:			
1 GHz	PE15A63000	55	3
	PE15A63001	55	4
	PE15A1011	54	52
	PE15A1049	54	53
	PE15A1012	54	54
	PE15A1013	54	55
	PE15A1052	54	56
1.3 GHz	PE15A1054	54	57
15 GHz	PE15A3037	52	98
	PE15A3036	51	8
20 GHz	PE15A4029	51	9
	PE15A3272	52	62
250 MHz	PE15A1043	54	47
3 GHz	PE1514	53	11
	PE1528	53	12
	PE1513	53	13
	PE15A1009	54	58
550 MHz	PE15A1044	54	48
6 GHz	PE15A4032	51	7
	PE15A3269	52	61
	PE15A8001	53	14
600 MHz	PE15A1063	54	49
800 MHz	PE15A1048	54	50
	PE15A1065	54	51
20 MHz to:			
1 GHz	PE15A1051	54	59
	PE15A1064	54	60
	PE15A5031	57	98
	PE15A5031F	57	99
	PE15A4072	55	25
	PE15A5057	55	26
1.5 GHz	PE15A1057	54	61

Frequency	Model No.	Page	C/R
20 MHz to:			
3 GHz	PE15A1008	54	62
	PE15A4017	55	27
4 GHz	PE15A1061	54	63
520 MHz	PE15A5065	55	24
30 MHz to:			
1.5 GHz	PE15A63002	55	5
	PE15A63003	55	6
2.5 GHz	PE15A5011	58	39
2.7 GHz	PE15B5003	51	1
	PE15A5086	58	40
20 GHz	PE15A3254	52	63
26.5 GHz	PE15A3312	52	64
3 GHz	PE15A4018	56	28
40 GHz	PE15A3023	51	10
40 MHz to:			
3 GHz	PE15A1060	54	64
50 MHz to:			
1 GHz	PE1517	53	15
	PE15A1050	54	65
	PE15A1014	54	66
	PE15A4009	56	29
1.2 GHz	PE15A1053	54	67
18 GHz	PE15A3900	52	96
2 GHz	PE1518	53	16
	PE15A1042	54	68
4 GHz	PE15A8000	53	17
40 GHz	PE15A3901	52	97
60 MHz to:			
6 GHz	PE15A4019	56	30
100 MHz to:			
12 GHz	PE15A3007	51	11

Frequency	Model No.	Page	C/R
100 MHz to:			
18 GHz	PE15A3255	52	65
	PE15A3256	52	66
	PE15A4052	56	31
	PE15A4052F	56	32
	PE15A7000	59	62
2 GHz	PE15A1066	54	69
26.5 GHz	PE15A3267	52	67
3 GHz	PE1516	53	18
6 GHz	PE15A5027	58	41
110 MHz to:			
10 GHz	PE15A3001	51	13
6 GHz	PE15A3004	51	12
200 MHz to:			
2.5 GHz	PE1525	53	19
2.6 GHz	PE15A5084	56	33
225 MHz to:			
512 MHz	PE15B5007	51	2
300 MHz to:			
18 GHz	PE15A3021	51	14
500 MHz to:			
1 GHz	PE15A5058	56	34
10 GHz	PE15A3005	51	20
18 GHz	PE15A3008	51	21
	PE15A3263	51	22
	PE15A2003	54	38
2 GHz	PE15A4038	51	15
	PE15A3014	51	16
	PE15A3015	51	17
	PE15A8004	53	20
	PE15A8005	53	21
	PE15A7001	59	63

See Our Website For Current Pricing & Real-Time Stock Availability!

Amplifiers Locator

Frequency	Model No.	Page	C/R
500 MHz to:			
2.5 GHz	PE15A4039	51	18
	PE15A5059	58	42
	PE15A5060	58	43
20 GHz	PE15A3253	52	68
3 GHz	PE15A1017	54	70
	PE15A1018	54	71
	PE15A5032	57	1
4 GHz	PE15A1068	54	72
	PE15A4053	56	35
	PE15A4053F	56	36
	PE15A7002	59	64
6 GHz	PE15A4037	51	19
700 MHz to:			
2.2 GHz	PE15A5004	57	2
2.7 GHz	PE15A1067	54	73
	PE15A5033	58	45
	PE15A5033F	58	46
6 GHz	PE15A5017	58	47
800 MHz to:			
1 GHz	PE15A5061	56	37
2 GHz	PE15A5035F	57	5
	PE15A5077	56	38
	PE15A5078	56	39
2.5 GHz	PE15A5020	57	6
4.2 GHz	PE15A5034F	56	40
	PE15A5034	56	41
	PE15A5062	58	48
5.5 GHz	PE15A3264	51	23
960 MHz	PE15A5040	57	3
	PE15A5041	57	4
820 MHz to:			
960 MHz	PE15A4026	56	42
860 MHz to:			
960 MHz	PE15A5042	57	7
	PE15A5039	57	8
900 MHz to:			
1.2 GHz	PE15A63004	55	7
	PE15A63005	55	8
1 GHz to:			
1.4 GHz	PE15A63006	55	9
12 GHz	PE15A1031	54	77
18 GHz	PE15A3262	51	24
	PE15A7009	59	65
2 GHz	PE15A6002	53	33
	PE15A1000	54	74
	PE15A1019	54	75
	PE15A4025	56	43
	PE15A4016	56	44
	PE15A5063	58	49
2.5 GHz	PE15A5036F	57	9
	PE15A5036	57	10
	PE15A5082	57	11
	PE15A5081	57	12
	PE15A5085	56	45
	PE15A5083	56	46
20 GHz	PE15A3500	53	1
	PE15A3512	53	2
	PE15A3513	53	3
23 GHz	PE15A1074	55	11
26.5 GHz	PE15A7010	59	66
3 GHz	PE15A5037	58	13
	PE15A5037F	58	14
	PE15A5026	58	50
4 GHz	PE1519	53	22
	PE15A1070	54	76
40 GHz	PE15A3514	53	4
	PE15A3515	53	5
	PE15A3595	53	6
	PE15A7011	59	67
7 GHz	PE15A1075	55	10
1.2 GHz to:			
1.4 GHz	PE15A1023	54	78
	PE15A1024	54	79
	PE15A1005	54	80
	PE15A5001	58	15
1.6 GHz	PE15A1028	54	81
	PE15A5064	59	51

Frequency	Model No.	Page	C/R
1.215 GHz to:			
1.4 GHz	PE15A1039	55	12
	PE15A1040	55	13
1.5 GHz to:			
3.5 GHz	PE15A5005	58	16
5 GHz	PE15A1034	54	82
1.7 GHz to:			
2.4 GHz	PE15A5073	58	17
2.5 GHz	PE15A5015	58	18
1.8 GHz to:			
4.2 GHz	PE15A3276	52	69
2 GHz to:			
12 GHz	PE15A4055	56	51
	PE15A4055F	56	52
18 GHz	PE15A4051	51	32
	PE15A3265	51	33
	PE15A3022	51	34
	PE15A3301	52	72
	PE15A3257	52	73
	PE15A3258	52	74
	PE1524	53	25
	PE15A1030	54	86
	PE15A4056	56	53
	PE15A4056F	56	54
	PE15A4057	56	55
	PE15A4057F	56	56
	PE15A5068	59	56
2.6 GHz	PE15A63007	55	14
	PE15A5074	56	47
20 GHz	PE15A4027	51	35
	PE15A4030	51	36
	PE15A3271	52	75
	PE15A3270	52	76
	PE15A4058	56	57
	PE15A4058F	56	58
24 GHz	PE15A3009	51	37
35 GHz	PE15A3038	51	38
4 GHz	PE1520	53	23
	PE15A6015	53	34
	PE15A1001	54	83
	PE15A1041	54	84
	PE15A5038	58	19
	PE15A5038F	58	20
4.4 GHz	PE15A4011	56	48
6 GHz	PE15A4040	51	25
	PE15A4041	51	26
	PE15A4003	51	27
	PE15A4005	51	28
	PE15A4042	51	29
	PE15A4043	51	30
	PE15A3503	52	53
	PE1521	53	24
	PE15A6007	53	35
	PE15A2001	54	39
	PE15A1010	54	85
	PE15A5047	58	21
	PE15A5047F	58	22
	PE15A5066	59	52
	PE15A5067	59	53
	PE15A5024	59	54
	PE15A5025	59	55
	PE15A7003	59	68
8 GHz	PE15A3016	51	31
	PE15A3290	52	70
	PE15A3291	52	71
	PE15A6008	53	36
	PE15A4054	56	49
	PE15A4054F	56	50
	PE15A7004	59	69
2.3 GHz to:			
2.7 GHz	PE15A5018	58	23
2.4 GHz to:			
2.5 GHz	PE15B5000	51	3
2.5 GHz to:			
4 GHz	PE15A5006	58	24
2.6 GHz to:			
3.1 GHz	PE15A63008	55	15
	PE15A63009	55	16

Frequency	Model No.	Page	C/R
2.6 GHz to:			
4.2 GHz	PE15A5007	58	25
3 GHz to:			
8 GHz	PE15A1035	54	87
3.1 GHz to:			
3.5 GHz	PE15A4046	51	39
	PE15A63010	55	17
	PE15A63011	55	18
	PE15A1006	55	88
	PE15A5003	58	26
	PE15A5002	56	59
3.5 GHz to:			
7 GHz	PE15A5008	58	27
	PE15A4012	56	60
4 GHz to:			
12 GHz	PE15A7005	59	70
8 GHz	PE1522	53	26
	PE15A1002	55	89
4.4 GHz to:			
4.9 GHz	PE15B5004	51	4
	PE15A5079	56	61
	PE15A5080	56	62
5.1 GHz	PE15B5005	51	5
5 GHz to:			
13 GHz	PE15A1073	55	19
9 GHz	PE15A9002	55	90
5.125 GHz to:			
5.875 GHz	PE15B5006	51	6
5.5 GHz to:			
9.5 GHz	PE15A5009	58	28
6 GHz to:			
10 GHz	PE15A5069	59	57
12 GHz	PE15A4044	51	40
	PE15A4045	51	41
	PE15A4001	51	42
	PE15A4004	51	43
	PE15A3506	52	54
	PE15A3505	52	55
	PE15A3292	52	77
	PE15A3293	52	78
	PE15A8006	53	27
	PE15A1032	55	91
	PE15A1072	55	92
	PE15A4060	56	63
	PE15A4060F	56	64
18 GHz	PE15A3018	51	44
	PE15A3019	51	45
	PE15A3017	51	46
	PE15A3020	51	47
	PE15A3295	52	79
	PE15A3294	52	80
	PE15A3302	52	81
	PE15A3259	52	82
	PE15A8007	53	28
	PE1523	53	29
	PE15A6012	53	37
	PE15A2004	54	40
	PE15A1071	55	93
	PE15A5050	58	29
	PE15A5050F	58	30
	PE15A5049	58	31
	PE15A5049F	58	32
	PE15A4061F	56	65
	PE15A4061	56	66
	PE15A5048	56	67
	PE15A5048F	56	68
	PE15A4062	56	69
	PE15A4062F	56	70
	PE15A5070	59	58
	PE15A7006	59	71
6.4 GHz to:			
7.1 GHz	PE15A5016	59	59
7 GHz to:			
11 GHz	PE15A1033	55	94
17 GHz	PE15A3273	52	83
7.5 GHz to:			
11 GHz	PE15A4013	56	71

Frequency	Model No.	Page	C/R
8 GHz to:			
11 GHz	PE15A4014	56	72
	PE15A4015	56	73
12 GHz	PE15A1027	55	95
	PE15A1026	55	96
	PE15A1003M	55	97
	PE15A1003	55	98
	PE15A1025	55	99
	PE15A5053	58	33
	PE15A5053F	58	34
	PE15A5052	58	35
	PE15A5051	56	74
	PE15A5051F	56	75
	PE15A4008	57	76
	PE15A5071	59	60
	PE15A5072	59	61
12.4 GHz	PE15A4063F	57	77
	PE15A4063	57	78
8.5 GHz to:			
10.5 GHz	PE15A5044	58	36
11 GHz	PE15A5043	58	37
	PE15A4006	57	79
	PE15A4007	57	80
12 GHz to:			
18 GHz	PE15A4002	51	48
	PE15A3507	52	56
	PE15A3296	52	84
	PE15A1004	55	1
12.4 GHz to:			
26.5 GHz	PE15A3024	51	49
14.4 GHz to:			
15.4 GHz	PE15A5021	57	81
17 GHz to:			
24 GHz	PE15A4028	51	50
27 GHz	PE15A3274	52	85
17.5 GHz to:			
21.5 GHz	PE15A4020	58	38
18 GHz to:			
26.5 GHz	PE15A3303	52	86
	PE15A3260	52	87
	PE15A4064	57	82
	PE15A4064F	57	83
	PE15A4021	57	84
	PE15A5054	57	85
	PE15A5054F	57	86
	PE15A7007	59	72
40 GHz	PE15A3025	51	51
	PE15A3268	52	88
	PE15A3304	52	89
	PE15A3305	52	90
	PE15A4065	57	87
	PE15A4065F	57	88
	PE15A7012	59	73
20 GHz to:			
40 GHz	PE15A3508	53	7
	PE15A3509	53	8
	PE15A3510	53	9
	PE15A3511	53	10
26.5 GHz to:			
40 GHz	PE15A4022	51	52
	PE15A3261	52	91
	PE15A3266	52	92
	PE15A3306	52	93
	PE15A3307	52	94
	PE15A3300	55	2
	PE15A4050	57	89
	PE15A4067	57	90
	PE15A4067F	57	91
	PE15A7008	59	74
29 GHz to:			
36 GHz	PE15A3275	52	95
30 GHz to:			
40 GHz	PE15A4069	57	92
	PE15A4069F	57	93

See Our Website For Current Pricing & Real-Time Stock Availability!

BI-DIRECTIONAL AMPLIFIERS

Amplifier Type	Frequency Band (GHz.)	Tx Gain (dB)	Gain Var. ±(dB)	P1dB (W) Linear	Rx P1dB (dBm)	Rx NF (dB)	DC Power Tx (V/mA)	ECCN	Model No	1	2-4	5-9	10+	ROW
Bi Directional, High Power	30 MHz - 2.7	36	2			2	12/1,400	EAR99	PE15B5003	$7,342.43	$6,901.88	$6,534.76	$6,241.07	1
Bi Directional	225 MHz - 512 MHz		0.5			2.5	28/1,600	5A991.G	PE15B5007	$13,456.59	$12,918.33	$12,380.06	$11,841.80	2
Bi Directional, High Power, High Rel	2.4 - 2.5	20		0.1	20		28/	EAR99	PE15B5000	$6,786.20	$6,514.75	$6,243.30	$5,971.86	3
Bi Directional	4.4 - 4.9	45	1			3.5	28/4,600	5A991.G	PE15B5004	$17,919.10	$17,202.34	$16,485.57	$15,768.81	4
	4.4 - 5.1	10				3	28/1,750	EAR99	PE15B5005	$15,409.38	$14,793.00	$14,176.63	$13,560.25	5
	5.125 - 5.875	43	1.25				28/2,500	EAR99	PE15B5006	$15,346.46	$14,732.60	$14,118.74	$13,504.88	6

BROADBAND AMPLIFIERS



Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1	2-4	5-9	10+	ROW
Broadband, High Rel	10 MHz - 6	24	0.75	5	29.5		15/740	EAR99	PE15A4032	$6,560.18	$6,297.77	$6,035.37	$5,772.96	7
	10 MHz - 15	12	0.3	4.5	28	29	14/360	EAR99	PE15A3036	$6,945.03	$6,667.23	$6,389.43	$6,111.63	8
	10 MHz - 20	13	0.75	3	23	25	15/225	EAR99	PE15A4029	$5,341.82	$5,128.15	$4,914.47	$4,700.80	9
Broadband	30 MHz - 40	25	2.5	6	20		11/400	EAR99	PE15A3023	$9,148.43	$8,782.49	$8,416.56	$8,050.62	10
	100 MHz - 12	18	1	3	25	28	12/300	EAR99	PE15A3007	$2,427.27	$2,330.18	$2,233.09	$2,136.00	11
	110 MHz - 6	11	1.25	6.5	27	30	12/300	EAR99	PE15A3004	$2,552.07	$2,449.99	$2,347.90	$2,245.82	12
	110 MHz - 10	10	1.5				12/300	EAR99	PE15A3001	$2,865.04	$2,750.44	$2,635.84	$2,521.24	13
	300 MHz - 18	37	2		30.5		15/750	EAR99	PE15A3021	$5,877.79	$5,642.68	$5,407.57	$5,172.46	14
Broadband, High Rel	500 MHz - 2	14	0.4	2.7	24		12/180	EAR99	PE15A4038	$1,073.26	$1,030.33	$987.40	$944.47	15
		30	0.6				12/240	EAR99	PE15A3014	$1,193.18	$1,145.45	$1,097.73	$1,050.00	16
		46	0.8				12/300	EAR99	PE15A3015	$1,433.65	$1,376.30	$1,318.96	$1,261.61	17
	500 MHz - 2.5	24	0.5	3.5			12/240	EAR99	PE15A4039	$1,358.18	$1,303.85	$1,249.53	$1,195.20	18
Broadband	500 MHz - 6				33	33	28/600	EAR99	PE15A4037	$4,579.26	$4,396.09	$4,212.92	$4,029.75	19
	500 MHz - 10	32	1	3	25		12/375	EAR99	PE15A3005	$2,871.90	$2,757.02	$2,642.15	$2,527.27	20
	500 MHz - 18	27	2.5				12/330	EAR99	PE15A3008	$3,360.29	$3,242.68	$3,125.07	$3,024.26	21
Broadband, High Rel		33	1.5	4	15		12/220	EAR99	PE15A3263	$2,577.15	$2,474.06	$2,370.98	$2,267.89	22
	800 MHz - 5.5	20	0.5		25	28	12/750	EAR99	PE15A3264	$1,642.96	$1,577.24	$1,511.52	$1,445.80	23
	1 - 18	30	1.5		19	20	12/240	EAR99	PE15A3262	$3,080.90	$2,957.66	$2,834.43	$2,711.19	24
	2 - 6	13	0.4	5.4	23		12/180	EAR99	PE15A4040	$1,629.29	$1,564.12	$1,498.95	$1,433.78	25
		22	0.6		27		12/420	EAR99	PE15A4041	$2,339.46	$2,245.88	$2,152.30	$2,058.72	26
		32	1	5	33		15/1,700	EAR99	PE15A4003	$3,990.31	$3,830.70	$3,671.09	$3,511.47	27
		33			30		12/1,000	EAR99	PE15A4005	$3,321.30	$3,188.45	$3,055.60	$2,922.74	28
		36	1.5	6	34		15/2,200	EAR99	PE15A4042	$3,863.74	$3,709.19	$3,554.64	$3,400.09	29
		44	1	4.5	35		12/4,200	EAR99	PE15A4043	$4,461.15	$4,282.70	$4,104.26	$3,925.81	30
	2 - 8	33	1.5		29.4		8.5/941	EAR99	PE15A3016	$2,769.87	$2,659.08	$2,548.28	$2,437.49	31
Broadband	2 - 18	12			16		12/65	EAR99	PE15A4051	$1,705.14	$1,636.93	$1,568.73	$1,500.52	32
Broadband, High Rel		33		3.5	13		12/180	EAR99	PE15A3265	$2,647.63	$2,541.72	$2,435.82	$2,329.91	33
Broadband		37			30.5		15/800	EAR99	PE15A3022	$5,550.00	$5,328.00	$5,106.00	$4,884.00	34
Broadband, High Rel	2 - 20	15	0.75		26		12/310	EAR99	PE15A4027	$6,258.74	$6,008.39	$5,758.04	$5,507.69	35
		31		3			15/400	EAR99	PE15A4030	$4,099.83	$3,935.84	$3,771.84	$3,607.85	36
Broadband	2 - 24	12		4		28	12/260	EAR99	PE15A3009	$2,218.54	$2,140.89	$2,063.24	$1,996.69	37
Broadband, High Rel	2 - 35		0.4		18	18.5	16/	3A001. B.4.C	PE15A3038	$7,509.75	$7,209.36	$6,908.97	$6,608.58	38
	3.1 - 3.5	30	0.7	4.5	30		12/900	EAR99	PE15A4046	$2,527.61	$2,426.51	$2,325.40	$2,224.30	39
	6 - 12	16	0.6	5	27		12/400	EAR99	PE15A4044	$2,146.52	$2,060.66	$1,974.80	$1,888.94	40
		28	0.8				12/500	EAR99	PE15A4045	$2,565.46	$2,462.84	$2,360.22	$2,257.60	41
		37	1.5	6	33		15/2,500	EAR99	PE15A4001	$3,849.56	$3,695.58	$3,541.60	$3,387.61	42
		38	1	5	30		15/1,300	EAR99	PE15A4004	$3,646.51	$3,500.65	$3,354.79	$3,208.93	43
	6 - 18	30		3.5	28		12/1,300	EAR99	PE15A3018	$3,243.78	$3,114.03	$2,984.28	$2,854.53	44
			1.5		30		18/1,700	EAR99	PE15A3019	$4,117.53	$3,952.83	$3,788.13	$3,623.43	45
		36	2		27		15/800	EAR99	PE15A3017	$3,489.75	$3,350.16	$3,210.57	$3,070.98	46
		42		5.4			12/900	EAR99	PE15A3020	$3,439.61	$3,302.03	$3,164.44	$3,026.86	47
	12 - 18	33		6	30		15/2,000	EAR99	PE15A4002	$3,933.34	$3,776.01	$3,618.67	$3,461.34	48
Broadband	12.4 - 26.5	35		3	24.5		12/500	EAR99	PE15A3024	$7,927.58	$7,610.48	$7,293.37	$6,976.27	49
Broadband, High Rel	17 - 24	22			24		12/250	EAR99	PE15A4028	$3,887.73	$3,732.22	$3,576.71	$3,421.20	50
Broadband	18 - 40	30	2.5	6.5	20		12/350	EAR99	PE15A3025	$6,853.53	$6,579.39	$6,305.25	$6,031.11	51
	26.5 - 40		2	6			12/350	EAR99	PE15A4022	$5,723.70	$5,494.75	$5,265.80	$5,036.86	52

See Our Website For Current Pricing & Real-Time Stock Availability!

BROADBAND AMPLIFIERS

Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
High Gain, High Rel	2 - 6	44	1	5	30		15/1,050	EAR99	PE15A3503	$3,212.43		See Web for Volume Pricing		53
	6 - 12	47	1.5	6	33		15/2,500	EAR99	PE15A3506	$4,146.29				54
		48	1	5	30		15/1,350	EAR99	PE15A3505	$3,492.58				55
	12 - 18	43	2	6			15/2,000	EAR99	PE15A3507	$3,925.62				56
Low Noise	0.01 MHz - 3	16	1.5	4	12		15/47	EAR99	PE15A3308	$784.33				57
	0.1 MHz - 10	33	6.5	5	13		12/110	EAR99	PE15A3311	$985.02				58
	0.3 MHz - 6.5	39	4.5	4	17		12/120	EAR99	PE15A3310	$950.74				59
	1 MHz - 3	21	1.5		22		15/110	EAR99	PE15A3309	$920.55				60
	10 MHz - 6	34	1	3	14.5		12/130	EAR99	PE15A3269	$663.13				61
Low Noise, High Rel	10 MHz - 20	15	0.5		22	24	12/195	EAR99	PE15A3272	$5,633.24				62
	30 MHz - 20		2.5		20		15/180	EAR99	PE15A3254	$3,444.54				63
	30 MHz - 26.5		2	5.5	16		15/230	EAR99	PE15A3312	$3,416.18				64
Low Noise	100 MHz - 18	14	1.5	3		18	12/80	EAR99	PE15A3255	$1,462.83				65
		28	2.5				12/160	EAR99	PE15A3256	$2,991.79				66
Low Noise, High Rel	100 MHz - 26.5	15	2	5	15		15/200	EAR99	PE15A3267	$5,414.68				67
	500 MHz - 20	14	1.75	3	14		15/75	EAR99	PE15A3253	$2,925.19				68
	1.8 - 4.2	26		1.2	15.5	17.5	12/105	EAR99	PE15A3276	$6,609.47				69
	2 - 8	14		2.5	13		12/120	EAR99	PE15A3290	$1,788.79				70
		30					12/150	EAR99	PE15A3291	$2,263.64				71
Low Noise	2 - 18	22	2.5	3.2			12/100	EAR99	PE15A3301	$5,609.59				72
		26	2	3	14		12/150	EAR99	PE15A3257	$1,892.38				73
		33	1				12/180	EAR99	PE15A3258	$2,332.82				74
Low Noise, High Rel	2 - 20	13	0.5	2	16	21	12/	EAR99	PE15A3271	$3,887.73				75
		15		2.5	13	15.5	12/78	EAR99	PE15A3270	$4,654.12				76
	6 - 12	17			7		12/100	EAR99	PE15A3292	$2,094.81				77
		30					12/200	EAR99	PE15A3293	$2,414.53				78
	6 - 18	14		3	13		12/100	EAR99	PE15A3295	$2,003.44				79
		30		2.5	10		12/200	EAR99	PE15A3294	$2,637.91				80
Low Noise		32	1.5	2.3	14		12/150	EAR99	PE15A3302	$5,473.63				81
		38	2	2.5	22		12/280	EAR99	PE15A3259	$1,687.09				82
Low Noise, High Rel	7 - 17	22			14		12/93	EAR99	PE15A3273	$3,887.73				83
	12 - 18	18		3.5	13		12/100	EAR99	PE15A3296	$1,931.87				84
	17 - 27	19		2.75	13.5		12/96	EAR99	PE15A3274	$5,934.97				85
Low Noise	18 - 26.5	32	2.5	2.3	11		12/250	EAR99	PE15A3303	$6,117.59				86
		40		2.5	13		12/150	EAR99	PE15A3260	$2,264.71				87
Low Noise, High Rel	18 - 40	18	2	5.5	10		15/250	3A001. B.4.C	PE15A3268	$7,925.95				88
Low Noise		32		4	12		12/200	EAR99	PE15A3304	$9,312.34				89
		44	4		11		12/250	EAR99	PE15A3305	$10,281.84				90
	26.5 - 40	22	1	3.5	13.5		12/125	EAR99	PE15A3261	$2,080.02				91
		30	2	2	11		12/150	EAR99	PE15A3266	$5,974.85				92
		35	2.5	2.4	10.5		12/150	EAR99	PE15A3306	$8,410.80				93
		52	3.5	3.3	12		12/375	EAR99	PE15A3307	$10,178.08				94
Low Noise, High Rel	29 - 36	20		2.9	11		3/80	EAR99	PE15A3275	$3,945.93				95

USB CONTROLLED BROADBAND AMPS.

Amplifier Type	Frequency Band (GHz.)	Gain (dB)	NF (dB)	P1dB (dBm)	Control	ECCN	Model No	1	2-4	5-9	10+	ROW
USB	50 MHz - 18	12	4.5	10	USB	EAR99	PE15A3900	$3,364.41	$3,229.83	$3,095.26	$2,960.68	96
	50 MHz - 40		5			EAR99	PE15A3901	$5,554.22	$5,332.05	$5,109.88	$4,887.71	97

BENCH-TOP AMPLIFIERS

Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	DC Power (Optional DC In) (V)	AC Power (V/Cycle)	ECCN	Model No	1	2-4	5-9	10+	ROW
Broadband, High Rel	10 MHz - 15	12	0.3	4	28	16/360		EAR99	PE15A3037	$6,762.00	$6,491.52	$6,221.04	$5,950.56	98

See Our Website For Current Pricing & Real-Time Stock Availability!

BENCH-TOP AMPLIFIERS

Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	DC Power (Optional DC In) (V)	AC Power (V/Cycle)	ECCN	Model No	1	2-4	5-9	10+	ROW
High Gain, High Rel	1 - 20	60	3	5	10		115/60	EAR99	PE15A3500	$13,056.69	$12,534.42	$12,012.15	$11,489.89	1
							100/	EAR99	PE15A3512	$11,787.62	$11,316.12	$10,844.61	$10,373.11	2
							220/	EAR99	PE15A3513	$12,524.34	$12,023.37	$11,522.39	$11,021.42	3
	1 - 40	40	2.5			12/	100/	EAR99	PE15A3514	$16,080.66	$15,437.43	$14,794.21	$14,150.98	4
							220/	EAR99	PE15A3515	$16,080.66	$15,437.43	$14,794.21	$14,150.98	5
					22		120/60	EAR99	PE15A3595	$16,731.16	$16,145.57	$15,559.98	$15,058.04	6
	20 - 40	30	2		10		100/60	EAR99	PE15A3508	$12,321.03	$11,828.19	$11,335.35	$10,842.51	7
							220/	EAR99	PE15A3509	$12,321.03	$11,828.19	$11,335.35	$10,842.51	8
		60	3				100/	EAR99	PE15A3510	$15,007.40	$14,407.10	$13,806.81	$13,206.51	9
							220/	EAR99	PE15A3511	$15,007.40	$14,407.10	$13,806.81	$13,206.51	10

GAIN BLOCK AMPLIFIERS

Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	IP3 (dBm)	DC Power (V/mA)	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
Gain Block	10 MHz - 3	12	10	5.5	10		15/40	EAR99	PE1514	$489.79		See Web for Volume Pricing		11
		15	2	3	11	12	18/40	EAR99	PE1528	$160.93				12
		20	14	2.7	13		15/50	EAR99	PE1513	$485.91				13
	10 MHz - 6	15	0.35	4.5	12	26	12/50	EAR99	PE15A8001	$753.78				14
	50 MHz - 1	22	0.75	3.5			12/150	EAR99	PE1517	$531.64				15
	50 MHz - 2		1				12/150	EAR99	PE1518	$663.80				16
	50 MHz - 4	26		5	22	35	12/120	EAR99	PE15A8000	$849.81				17
	100 MHz - 3	18	18	6	16		15/120	EAR99	PE1516	$564.00				18
	200 MHz - 2.5	22	1.25		15		15/120	EAR99	PE1525	$562.28				19
Gain Block, High Rel	500 MHz - 2	17	0.4	1.8		25	12/70	EAR99	PE15A8004	$965.94				20
		50	1.8				12/180	EAR99	PE15A8005	$1,282.73				21
Gain Block	1 - 4	26	0.5	2.5	15		12/120	EAR99	PE1519	$1,045.47				22
	2 - 4	25					12/120	EAR99	PE1520	$1,086.20				23
	2 - 6	26		3			12/120	EAR99	PE1521	$917.09				24
	2 - 18	23	1	3.5	13		12/150	EAR99	PE1524	$1,313.73				25
	4 - 8	26	0.5	3	15		12/100	EAR99	PE1522	$1,126.13				26
Gain Block, High Rel	6 - 12	12	0.4	2.3	10	20	12/80	EAR99	PE15A8006	$1,433.65				27
	6 - 18	17	0.6	4.5	20		12/160	EAR99	PE15A8007	$1,999.56				28
Gain Block		22	1		13		12/150	EAR99	PE1523	$1,493.50				29

DC COUPLED AMPLIFIERS

Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	IP3 (dBm)	DC Power (V/mA)	ECCN	Model No	1-4	5-9	10-24	25+	ROW
DC Coupled	DC - 17 MHz	30			14	25	/45	EAR99	PE15A86002	$637.59	$605.71	$573.83	$548.33	30
	DC - 1.5	14			11		/45	EAR99	PE15A86001	$920.55	$874.52	$828.50	$791.67	31
	DC - 2	8		16			12/45	EAR99	PE15A86000	$885.99	$841.69	$797.39	$761.95	32

LIMITING AMPLIFIERS

Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	Input Power (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1	2-4	5-9	10+	ROW
Limitings, High Rel	1 - 2	60	3	3	-40 to 10	19	13/250	EAR99	PE15A6002	$2,421.09	$2,324.25	$2,227.40	$2,130.56	33
	2 - 4	40			-20 to 10		15/200	EAR99	PE15A6015	$2,468.50	$2,369.76	$2,271.02	$2,172.28	34
	2 - 6	80	3	4	-61 to 10	15	13/550	EAR99	PE15A6007	$3,103.42	$2,979.28	$2,855.15	$2,731.01	35
	2 - 8	40	2	5	-20 to 20	19	13/300	EAR99	PE15A6008	$2,386.50	$2,291.04	$2,195.58	$2,100.12	36
	6 - 18			4			13/300	EAR99	PE15A6012	$2,905.00	$2,788.80	$2,672.60	$2,556.40	37

See Our Website For Current Pricing & Real-Time Stock Availability!

LOG AMPLIFIERS

Amplifier Type	Frequency Band (GHz.)	Typ Recovery Time (ns)	Min TSS (dBm)	Log Linearity ± (dB)	Log Range (dBm)	Rise Time (ns)	Log Slope (mV/dB)	ECCN	Model No	1	2-4	5-9	10+	ROW
Log, High Rel	500 MHz - 18	150	-65	1.75	-65 to 5	20	20	EAR99	PE15A2003	$17,303.47	$16,611.33	$15,919.19	$15,227.05	38
	2 - 6	60	-73		-70 to 5	15	40	EAR99	PE15A2001	$11,009.25	$10,568.88	$10,128.51	$9,688.14	39
	6 - 18	150	-40	1	-40 to 0	20	50	EAR99	PE15A2004	$8,118.03	$7,793.31	$7,468.59	$7,143.87	40

LOW NOISE AMPLIFIERS

Standard



Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	IP3 (dBm)	DC Power (V/mA)	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
Low Noise	0.009 MHz - 3	32	1.25	2.5	16	29	15/110	EAR99	PE15A1007	$457.08	See Web for Volume Pricing			41
	0.01 MHz - 500 MHz	45	0.5		11	23	16/75	EAR99	PE15A1046	$719.51				42
	0.01 MHz - 1.4	42	1	3	19	32	16/120	EAR99	PE15A1055	$836.76				43
	0.01 MHz - 2	28	2	3.2	13	23	18/45	EAR99	PE15A1059	$606.34				44
	0.03 MHz - 600 MHz	50	1.2	2.2	14	24	18/85	EAR99	PE15A1047	$909.51				45
	1 MHz - 500 MHz	33.5	1.5	2	13		30/40	EAR99	PE15A1045	$606.34				46
	10 MHz - 250 MHz	17	0.5	1.4	22	39	5.25/160	EAR99	PE15A1043	$836.76				47
	10 MHz - 550 MHz	29.7	0.3	1.7	19	34	15/105	EAR99	PE15A1044	$759.96				48
	10 MHz - 600 MHz	40.5	0.8	0.9			15/140	EAR99	PE15A1063	$1,216.71				49
	10 MHz - 800 MHz	42	0.7	2	17	30	15/100	EAR99	PE15A1048	$720.63				50
		60	1.5	2.1		27	15/160	EAR99	PE15A1065	$1,358.18				51
	10 MHz - 1	30	0.7	1			15/110	EAR99	PE15A1011	$502.39				52
		32		2	12	23	15/40	EAR99	PE15A1049	$540.47				53
High Gain		40	1	0.8	17	31.5	15/110	EAR99	PE15A1012	$481.12				54
		50	1.25	1	18	28	15/140	EAR99	PE15A1013	$569.87				55
Low Noise		51	0.8	2.2	13	22	15/88	EAR99	PE15A1052	$824.41				56
	10 MHz - 1.3	35	0.5	1.5	20	34	15/165	EAR99	PE15A1054	$990.35				57
	10 MHz - 3	34	0.75	1.4	11	25	15/95	EAR99	PE15A1009	$738.40				58
	20 MHz - 1	30	0.5	1.3	18	32	18/140	EAR99	PE15A1051	$793.47				59
		30.5	0.8		19	34	15/140	EAR99	PE15A1064	$1,216.71				60
	20 MHz - 1.5	20	1.2	1	17	35	18/70	EAR99	PE15A1057	$719.51				61
	20 MHz - 3	25	0.75	1.6	13.5	25	15/75	EAR99	PE15A1008	$685.54				62
	20 MHz - 4		0.7	2	18	34	5.5/160	EAR99	PE15A1061	$1,026.72				63
	40 MHz - 3	16	1.6	1.3	7	22	3.3/18	EAR99	PE15A1060	$731.43				64
	50 MHz - 1	18	0.5	1	16	32	18/70	EAR99	PE15A1050	$682.29				65
		19			18	36	12/90	EAR99	PE15A1014	$303.05				66
	50 MHz - 1.2	47	1	2.2	13	23	15/88	EAR99	PE15A1053	$836.76				67
	50 MHz - 2	27	0.75	1.8	22	37	13.5/160	EAR99	PE15A1042	$692.87				68
	100 MHz - 2	61.5	1	2.5	19	33	15/170	EAR99	PE15A1066	$1,483.48				69
	500 MHz - 3	14.5	0.4	2	20	35	12/90	EAR99	PE15A1017	$354.50				70
		29	1	2.6		34	12/190	EAR99	PE15A1018	$448.62				71
	500 MHz - 4	24	2.5	0.7	17		15/65	EAR99	PE15A1068	$836.76				72
	700 MHz - 2.7	23	1		18	35	15/65	EAR99	PE15A1067	$836.76				73
Low Noise, High Rel	1 - 2	35		1.5	10		13/200	EAR99	PE15A1000	$1,332.30				74
High Gain		40		0.8	11	25	12/120	EAR99	PE15A1019	$1,059.33				75
Low Noise	1 - 4	20	1.2		20	41	15/120	EAR99	PE15A1070	$836.76				76
Low Noise, High Rel	1 - 12	16		1.75	17		6/60	EAR99	PE15A1031	$5,588.46				77
	1.2 - 1.4	25	0.75	1.5	10		13.2/150	EAR99	PE15A1023	$632.48				78
		35			17		13.2/180	EAR99	PE15A1024	$709.12				79
High Gain, High Rel		40			15		13.2/200	EAR99	PE15A1005	$1,180.72				80
Low Noise	1.2 - 1.6		0.5	0.8	12		15/100	EAR99	PE15A1028	$679.09				81
Low Phase Noise, High Rel	1.5 - 5	14		4.5	17	27	9/170	EAR99	PE15A1034	$6,101.05				82
Low Noise, High Rel	2 - 4	38	1	2	13		13/200	EAR99	PE15A1001	$1,589.37				83
Low Noise		40		0.7	14		15/100	EAR99	PE15A1041	$1,073.26				84
High Gain	2 - 6			0.9		25	15/110	EAR99	PE15A1010	$1,086.68				85
Low Phase Noise, High Rel	2 - 18	12.5		6.5	13		5/80	EAR99	PE15A1030	$10,151.46				86
	3 - 8	11		6	14	25	7/250	EAR99	PE15A1035	$6,101.05				87

See Our Website For Current Pricing & Real-Time Stock Availability!

Standard

Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	IP3 (dBm)	DC Power (V/mA)	ECCN	Model No	1	2-4	5-9	10+	ROW
High Gain, High Rel	3.1 - 3.5	40	0.3	1.1	15		17/150	EAR99	PE15A1006	$1,953.88	$1,875.72	$1,797.57	$1,719.41	88
Low Noise, High Rel	4 - 8	38	1	2	13		13/250	EAR99	PE15A1002	$1,948.14	$1,870.21	$1,792.29	$1,714.36	89
	5 - 9	22.5		1.75	14.8	25	12/105	EAR99	PE15A9002	$7,257.75	$6,967.44	$6,677.13	$6,386.82	90
Low Phase Noise, High Rel	6 - 12	11	1	4.5	20	34	7/200	EAR99	PE15A1032	$6,433.88	$6,176.52	$5,919.17	$5,661.81	91
Low Noise		25	0.7	2.1	11	25	5.5/65	EAR99	PE15A1072	$1,633.07	$1,567.75	$1,502.42	$1,437.10	92
	6 - 18	26	2.5	1.9			5.5/65	EAR99	PE15A1071	$1,709.85	$1,641.46	$1,573.06	$1,504.67	93
Low Phase Noise, High Rel	7 - 11	9		6	22	33	7/300	EAR99	PE15A1033	$7,224.46	$6,935.48	$6,646.50	$6,357.52	94
Low Noise, High Rel	8 - 12	18	1	2.2	13		13/150	EAR99	PE15A1027	$1,697.72	$1,629.81	$1,561.90	$1,493.99	95
		28					13/200	EAR99	PE15A1026	$2,072.88	$1,989.96	$1,907.05	$1,824.13	96
		38					13/250	EAR99	PE15A1003M	$2,063.70	$1,981.15	$1,898.60	$1,816.06	97
							13/250	EAR99	PE15A1003	$2,304.22	$2,212.05	$2,119.88	$2,027.71	98
		48					13/300	EAR99	PE15A1025	$2,452.85	$2,354.74	$2,256.62	$2,158.51	99
	12 - 18	38		3	13		13/300	EAR99	PE15A1004	$2,518.20	$2,417.47	$2,316.74	$2,216.02	1
Low Noise	26.5 - 40	43	2	2	12	20	15/110	EAR99	PE15A3300	$3,366.75	$3,232.08	$3,097.41	$2,962.74	2

Input Protected

Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	IP3 (dBm)	DC Power (V/mA)	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
Input Protected Low Noise	10 MHz - 1	30	0.7	1	17	32	15/120	EAR99	PE15A63000	$718.42		See Web for Volume Pricing		3
		40	1			31.5	15/110	EAR99	PE15A63001	$714.41				4
	30 MHz - 1.5	25	0.5	1.6	22	39	15/150	EAR99	PE15A63002	$664.39				5
		29			23		15/160	EAR99	PE15A63003	$664.39				6
	900 MHz - 1.2	30	1	1.2	10		12/100	EAR99	PE15A63004	$622.51				7
		40					12/100	EAR99	PE15A63005	$622.51				8
	1 - 1.4	30					12/110	EAR99	PE15A63006	$622.51				9
GaN Input Protected Low Noise	1 - 7	42	3.5	1.5	22	31	28/200	EAR99	PE15A1075	$6,211.34				10
	1 - 23	29	1.5	3.5	20	32	28/250	EAR99	PE15A1074	$5,806.63				11
Integrated Band Pass Filter Low Noise	1.215 - 1.4	25	0.75	0.5	16		12/130	EAR99	PE15A1039	$1,018.07				12
		35					12/130	EAR99	PE15A1040	$943.18				13
Input Protected Low Noise	2 - 2.6	30	0.35	0.85	12		15/110	EAR99	PE15A63007	$971.79				14
	2.6 - 3.1		1	1.2	10		12/120	EAR99	PE15A63008	$962.62				15
		40					12/120	EAR99	PE15A63009	$869.35				16
	3.1 - 3.5	28	0.5	0.8	8	20	15/45	EAR99	PE15A63010	$869.35				17
		35	1	0.85	13		12/100	EAR99	PE15A63011	$916.78				18
GaN Input Protected Low Noise	5 - 13	44	2.5	1.8	22	31	28/160	EAR99	PE15A1073	$6,580.85				19

POWER AMPLIFIERS (<4W)

Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
High Power, Class AB	1 MHz - 1	36	1.5		33	36	28/1,200	EAR99	PE15A5030	$3,087.89		See Web for Volume Pricing		20
High Power, Class AB, Power with Fan							28/1,700	EAR99	PE15A5030F	$3,879.26				21
High Power, Class AB	1.5 MHz - 30 MHz	47	2			47	28/5,000	EAR99	PE15A5055	$5,273.60				22
	1.5 MHz - 100 MHz						28/5,000	EAR99	PE15A5056	$6,798.00				23
	20 MHz - 520 MHz	51				50	28/9,000	EAR99	PE15A5065	$6,384.04				24
Power	20 MHz - 1	40	0.5	6			24/630	EAR99	PE15A4072	$2,165.53				25
High Power, Class AB		49	2			49	28/11,000	EAR99	PE15A5057	$7,814.28				26
Power	20 MHz - 3	27	0.75		30		12/220	EAR99	PE15A4017	$848.39				27

See Our Website For Current Pricing & Real-Time Stock Availability!

POWER AMPLIFIERS (<4W)

Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
Power	30 MHz - 3	38	1		30		12/270	EAR99	PE15A4018	$973.42				28
	50 MHz - 1	26	0.75	5	28		12/450	EAR99	PE15A4009	$1,379.13				29
	60 MHz - 6	36	1.5		29		15/530	EAR99	PE15A4019	$2,718.96				30
High Rel	100 MHz - 18	25	3	8			15/1,000	EAR99	PE15A4052	$11,591.93				31
High Rel, Power with Fan							15/2,160	EAR99	PE15A4052F	$11,266.88				32
Power, Class AB	200 MHz - 2.6	46	4		33	10	28/1,400	EAR99	PE15A5084	$10,940.75				33
High Power, Class AB	500 MHz - 1	50	2			50	28/10,000	EAR99	PE15A5058	$6,798.00				34
High Rel	500 MHz - 4	30	3	6	30		12/1,500	EAR99	PE15A4053	$4,066.98				35
High Rel, Power with Fan							12/2,660	EAR99	PE15A4053F	$4,985.53				36
High Power, Class AB	800 MHz - 1	53	2			53	28/25,000	EAR99	PE15A5061	$6,798.00				37
Power, Class AB	800 MHz - 2	55	2.5		31	46	28/3,000	EAR99	PE15A5077	$11,462.49				38
Power, Class AB, Power with Fan		60	5		33		28/3,000	EAR99	PE15A5078	$12,725.63				39
	800 MHz - 4.2	31	2		30.8	31.8	13/1,000	EAR99	PE15A5034F	$3,110.21				40
Power, Class AB							13/800	EAR99	PE15A5034	$1,954.96				41
Power	820 MHz - 960 MHz	15	0.5	2	30		12/500	EAR99	PE15A4026	$547.65				42
	1 - 2	35	0.75	1.5	33		12/600	EAR99	PE15A4025	$1,381.65				43
High Power					36		12/800	EAR99	PE15A4016	$1,613.89				44
Power, Class AB	1 - 2.5	14	3			20	28/2,200	EAR99	PE15A5085	$9,330.62				45
		45	4		33	7	28/650	EAR99	PE15A5083	$10,312.99				46
	2 - 2.6	54	2.5		31	30	28/2,400	EAR99	PE15A5074	$9,854.74				47
High Power	2 - 4.4	32	0.5	10	36	37		EAR99	PE15A4011	$2,508.51				48
High Rel	2 - 8	38	2.5	5.5	30		12/1,200	EAR99	PE15A4054	$5,741.95				49
High Rel, Power with Fan							12/2,360	EAR99	PE15A4054F	$6,928.48	See Web for Volume Pricing			50
High Rel	2 - 12	35	4		33		15/4,500	EAR99	PE15A4055	$13,323.78				51
High Rel, Power with Fan							15/5,660	EAR99	PE15A4055F	$15,314.82				52
High Rel	2 - 18	30	2.5		30		12/2,500	EAR99	PE15A4056	$12,074.18				53
High Rel, Power with Fan							12/3,660	EAR99	PE15A4056F	$13,005.48				54
Power			4		33		12/5,000	EAR99	PE15A4057	$14,151.92				55
Power with Fan							12/6,160	EAR99	PE15A4057F	$15,025.89				56
High Rel	2 - 20		5.5		31		12/4,500	EAR99	PE15A4058	$14,526.47				57
High Rel, Power with Fan							12/5,660	EAR99	PE15A4058F	$14,341.03				58
High Power	3.1 - 3.5	45	1.5	4		40	15/5,000	EAR99	PE15A5002	$3,162.44				59
	3.5 - 7	26	2	11	36	37	/1,600	EAR99	PE15A4012	$3,106.52				60
Power, Class AB, Power with Fan	4.4 - 4.9	48	5		33	20	28/3,600	5A991.G	PE15A5079	$15,310.66				61
							28/3,600	5A991.G	PE15A5080	$17,230.20				62
High Rel	6 - 12	47	2.5	6.5	30.5		12/1,500	EAR99	PE15A4060	$5,015.70				63
High Rel, Power with Fan							12/2,660	EAR99	PE15A4060F	$6,678.92				64
	6 - 18	30		7	27		12/1,380	EAR99	PE15A4061F	$6,614.54				65
High Rel							12/800	EAR99	PE15A4061	$5,851.47				66
		35	3.5		33		12/2,500	EAR99	PE15A5048	$11,313.43				67
High Rel, Power with Fan							12/3,660	EAR99	PE15A5048F	$12,263.06				68
High Rel		38		10	30		12/1,800	EAR99	PE15A4062	$10,060.03				69
High Rel, Power with Fan							12/2,960	EAR99	PE15A4062F	$11,072.50				70
High Power	7.5 - 11	25	2		33	37		EAR99	PE15A4013	$2,510.32				71
Power	8 - 11				31	34		EAR99	PE15A4014	$2,115.01				72
High Power		28	3		32	36		EAR99	PE15A4015	$2,145.64				73
High Rel	8 - 12	30	2		33		12/2,500	EAR99	PE15A5051	$6,899.53				74
High Rel, Power with Fan							12/3,660	EAR99	PE15A5051F	$8,067.33				75

See Our Website For Current Pricing & Real-Time Stock Availability!

POWER AMPLIFIERS (<4W)

Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1	2-4	5-9	10+	ROW
Power	8 - 12	41	1	3.5	30	31	12/1,200	EAR99	PE15A4008	$3,586.61	$3,443.15	$3,299.68	$3,156.22	76
High Rel, Power with Fan	8 - 12.4	30	1.75	6	27		12/1,380	EAR99	PE15A4063F	$4,988.63	$4,789.08	$4,589.54	$4,389.99	77
High Rel							12/800	EAR99	PE15A4063	$4,277.44	$4,106.34	$3,935.24	$3,764.15	78
Power	8.5 - 11		0.5	3	30		15/900	EAR99	PE15A4006	$2,913.62	$2,797.08	$2,680.53	$2,563.99	79
			0.75	5	36		12/4,500	EAR99	PE15A4007	$3,996.87	$3,837.00	$3,677.12	$3,517.25	80
	14.4 - 15.4	43	0.5		34.8		15/1,500	EAR99	PE15A5021	$8,049.45	$7,727.47	$7,405.49	$7,083.52	81
High Rel	18 - 26.5	28	2.5	7	27		12/1,150	EAR99	PE15A4064	$9,795.30	$9,403.49	$9,011.68	$8,619.86	82
High Rel, Power with Fan							12/1,730	EAR99	PE15A4064F	$10,344.63	$9,930.84	$9,517.06	$9,103.27	83
Power		33	1.25	5	31		12/1,800	EAR99	PE15A4021	$4,425.55	$4,248.53	$4,071.51	$3,894.48	84
High Rel		35	3		33		12/3,500	EAR99	PE15A5054	$13,125.15	$12,600.14	$12,075.14	$11,550.13	85
High Rel, Power with Fan							12/4,660	EAR99	PE15A5054F	$13,239.92	$12,710.32	$12,180.73	$11,651.13	86
High Rel	18 - 40		4	9	23		12/1,000	EAR99	PE15A4065	$11,612.38	$11,147.88	$10,683.39	$10,218.89	87
High Rel, Power with Fan							12/1,580	EAR99	PE15A4065F	$11,854.98	$11,380.78	$10,906.58	$10,432.38	88
Power	26.5 - 40		3	4.5	20	22	12/270	EAR99	PE15A4050	$3,206.44	$3,078.18	$2,949.92	$2,821.67	89
High Rel			4	10		27	12/3,000	EAR99	PE15A4067	$13,206.00	$12,743.79	$12,281.58	$11,885.40	90
High Rel, Power with Fan							12/3,160	EAR99	PE15A4067F	$14,311.43	$13,810.53	$13,309.63	$12,880.29	91
High Rel	30 - 40	20	2			20	12/350	EAR99	PE15A4069	$8,310.61	$7,978.19	$7,645.76	$7,313.34	92
High Rel, Power with Fan							12/930	EAR99	PE15A4069F	$8,919.80	$8,563.01	$8,206.22	$7,849.42	93

HIGH POWER AMPLIFIERS (>4W)

Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1	2-4	5-9	10+	ROW
High Power, Class AB	0.15 MHz - 230 MHz	43	1.5		41.8	44	28/5,000	EAR99	PE15A5028	$4,904.86	$4,708.67	$4,512.47	$4,316.28	94
							28/5,500	EAR99	PE15A5028F	$5,305.50	$5,093.28	$4,881.06	$4,668.84	95
High Power, Class AB, Power with Fan	0.5 MHz - 500 MHz	44			40	39	28/2,000	EAR99	PE15A5029	$2,589.71	$2,486.12	$2,382.53	$2,278.94	96
							28/2,000	EAR99	PE15A5029F	$2,758.17	$2,647.84	$2,537.52	$2,427.19	97
High Power, Class AB	20 MHz - 1	46				44	28/5,200	EAR99	PE15A5031	$4,085.84	$3,922.41	$3,758.97	$3,595.54	98
High Power, Class AB, Power with Fan							28/5,800	EAR99	PE15A5031F	$4,864.42	$4,669.84	$4,475.27	$4,280.69	99
High Power, Class AB	500 MHz - 3	48	2		44	47	36/8,333	EAR99	PE15A5032	$16,016.50	$15,375.84	$14,735.18	$14,094.52	1
High Power	700 MHz - 2.2	30		10	38	38.5		EAR99	PE15A5004	$2,484.22	$2,397.27	$2,310.32	$2,235.80	2
	800 MHz - 960 MHz		1	3			12/1,800	EAR99	PE15A5040	$1,395.54	$1,339.72	$1,283.90	$1,228.08	3
		37					12/1,800	EAR99	PE15A5041	$1,463.45	$1,404.91	$1,346.37	$1,287.84	4
High Power, Class AB	800 MHz - 2	41	1.5		40	40.8	13/5,500	EAR99	PE15A5035F	$5,017.69	$4,816.98	$4,616.27	$4,415.57	5
High Power, Class A	800 MHz - 2.5	40	2		41		12/5,500	EAR99	PE15A5020	$5,129.12	$4,923.96	$4,718.79	$4,513.63	6
High Power	860 MHz - 960 MHz	42	1	3.5		42.5	12/2,800	EAR99	PE15A5042	$2,977.14	$2,858.05	$2,738.97	$2,619.88	7
					44		12/6,500	EAR99	PE15A5039	$4,248.38	$4,078.44	$3,908.51	$3,738.57	8
High Power, Class AB, Power with Fan	1 - 2.5	40	1.5		39	40	13/5,500	EAR99	PE15A5036F	$5,444.46	$5,226.68	$5,008.90	$4,791.12	9
High Power, Class AB		44			41		13/5,000	EAR99	PE15A5036	$4,477.46	$4,298.36	$4,119.26	$3,940.16	10
Power, Class AB, Power with Fan		47	3		38	18	28/1,900	EAR99	PE15A5082	$12,669.13	$12,162.36	$11,655.60	$11,148.83	11
Power, Class AB		50					28/1,900	EAR99	PE15A5081	$10,792.23	$10,360.54	$9,928.85	$9,497.16	12

See Our Website For Current Pricing & Real-Time Stock Availability!

HIGH POWER AMPLIFIERS (>4W)

Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1	2-4	5-9	10+	ROW
High Power, Class AB	1 - 3	44	1.5		37.8	39	13/3,000	EAR99	PE15A5037	$5,519.84	$5,299.05	$5,078.25	$4,857.46	13
High Power, Class AB, Power with Fan							13/4,000	EAR99	PE15A5037F	$6,554.80	$6,292.61	$6,030.42	$5,768.22	14
High Power	1.2 - 1.4	40	0.3		40		12/4,000	EAR99	PE15A5001	$4,323.37	$4,150.44	$3,977.50	$3,804.57	15
	1.5 - 3.5	20	1.25	10	38.5	39		EAR99	PE15A5005	$2,636.59	$2,531.13	$2,425.66	$2,320.20	16
Power, Class AB	1.7 - 2.4	54	3		42	35	28/3,600	EAR99	PE15A5073	$9,395.13	$9,019.32	$8,643.52	$8,267.71	17
High Power	1.7 - 2.5	11	0.5		37		12/800	EAR99	PE15A5015	$2,646.46	$2,540.60	$2,434.74	$2,328.88	18
Power, Class AB	2 - 4	39	1.5		37.8	39	13/3,000	EAR99	PE15A5038	$5,709.75	$5,481.36	$5,252.97	$5,024.58	19
							13/5,500	EAR99	PE15A5038F	$6,128.78	$5,883.63	$5,638.48	$5,393.33	20
High Rel	2 - 6	40	3.5		37		12/7,000	EAR99	PE15A5047	$11,637.22	$11,171.73	$10,706.24	$10,240.75	21
High Rel, Power with Fan							12/8,160	EAR99	PE15A5047F	$12,747.77	$12,237.86	$11,727.95	$11,218.04	22
High Power	2.3 - 2.7	55	0.5		41.5		12/5,500	EAR99	PE15A5018	$6,082.67	$5,839.36	$5,596.06	$5,352.75	23
	2.5 - 4	19		8	38	38.5		EAR99	PE15A5006	$1,680.70	$1,613.47	$1,546.24	$1,479.02	24
	2.6 - 4.2		1	9	39	39		EAR99	PE15A5007	$1,746.25	$1,676.40	$1,606.55	$1,536.70	25
	3.1 - 3.5	47	1.5	3.5	43		12/9,000	EAR99	PE15A5003	$4,323.37	$4,150.44	$3,977.50	$3,804.57	26
	3.5 - 7	19	2	12	37	38		EAR99	PE15A5008	$3,498.52	$3,358.58	$3,218.64	$3,078.70	27
	5.5 - 9.5	24		8.5				EAR99	PE15A5009	$3,074.14	$2,951.17	$2,828.21	$2,705.24	28
High Rel	6 - 18	40	5		40		12/13,000	EAR99	PE15A5050	$21,007.15	$20,271.90	$19,536.65	$18,906.44	29
High Rel, Power with Fan							15/14,160	EAR99	PE15A5050F	$23,430.44	$22,610.37	$21,790.31	$21,087.40	30
High Rel		41			37		12/7,500	EAR99	PE15A5049	$17,697.50	$17,078.09	$16,458.68	$15,927.75	31
High Rel, Power with Fan							12/8,660	EAR99	PE15A5049F	$19,109.37	$18,440.54	$17,771.71	$17,198.43	32
High Rel	8 - 12	30	2.5		40		12/14,000	EAR99	PE15A5053	$17,547.81	$16,933.64	$16,319.46	$15,793.03	33
High Rel, Power with Fan							12/15,160	EAR99	PE15A5053F	$18,655.88	$18,002.92	$17,349.97	$16,790.29	34
High Rel		40	2		37		12/6,000	EAR99	PE15A5052	$13,014.04	$12,493.48	$11,972.92	$11,452.36	35
High Power	8.5 - 10.5	36	1.5		38.5		12/4,000	EAR99	PE15A5044	$4,829.08	$4,635.92	$4,442.75	$4,249.59	36
	8.5 - 11	30	0.75	5			12/7,500	EAR99	PE15A5043	$5,044.05	$4,842.29	$4,640.53	$4,438.76	37
	17.5 - 21.5	40	1.5		37		12/3,500	EAR99	PE15A4020	$4,773.72	$4,582.77	$4,391.82	$4,200.87	38

GaN HIGH POWER AMPLIFIERS

Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1	2-4	5-9	10+	ROW
High Power	30 MHz - 2.5	43	2			40	12/2,800	EAR99	PE15A5011	$8,575.35	$8,232.34	$7,889.32	$7,546.31	39
	30 MHz - 2.7	35	1.5			39	/1,400	EAR99	PE15A5086	$11,642.43	$11,176.73	$10,711.04	$10,245.34	40
	100 MHz - 6	60	1.25	10		40	28/2,200	EAR99	PE15A5027	$19,358.10	$18,583.78	$17,809.45	$17,035.13	41
High Power, Class AB	500 MHz - 2.5	48	2			47	28/7,000	EAR99	PE15A5059	$5,673.15	$5,332.76	$5,049.10	$4,822.18	42
		50				50	28/13,000	EAR99	PE15A5060	$12,974.58	$12,196.11	$11,547.38	$11,028.39	43
	500 MHz - 3	48			44	47	36/8,333	EAR99	PE15A5032	$16,016.50	$15,375.84	$14,735.18	$14,094.52	44
High Power, Class AB, Power with Fan	700 MHz - 2.7	45	1.5			50	30/8,733	EAR99	PE15A5033	$15,177.59	$14,570.49	$13,963.38	$13,356.28	45
							30/8,733	EAR99	PE15A5033F	$15,645.44	$15,019.62	$14,393.80	$13,767.99	46
High Power	700 MHz - 6	43	2			40	32/2,000	EAR99	PE15A5017	$9,969.23	$9,570.46	$9,171.69	$8,772.92	47
High Power, Class AB	800 MHz - 4.2	47				47	28/13,000	EAR99	PE15A5062	$8,845.71	$8,314.97	$7,872.68	$7,518.85	48
	1 - 2	53	1.5			53	28/20,000	EAR99	PE15A5063	$10,358.38	$9,736.88	$9,218.96	$8,804.62	49
High Power	1 - 3	50	1.25	10		47	28/4,000	EAR99	PE15A5026	$19,201.56	$18,433.50	$17,665.44	$16,897.37	50

See Our Website For Current Pricing & Real-Time Stock Availability!

GaN HIGH POWER AMPLIFIERS

Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	P1dB (dBm)	Psat (dBm)	DC Power (V/mA)	ECCN	Model No	1	2-4	5-9	10+	ROW
High Power, Class AB	1.2 - 1.6	48	2.5			47	28/8,000	EAR99	PE15A5064	$4,837.58	$4,547.33	$4,305.45	$4,111.94	51
	2 - 6	43	2			43	28/5,000	EAR99	PE15A5066	$8,624.71	$8,107.23	$7,675.99	$7,331.00	52
		46				46	28/6,000	EAR99	PE15A5067	$14,135.03	$13,286.93	$12,580.18	$12,014.78	53
High Power		50	1.25	7		44	28/3,000	EAR99	PE15A5024	$15,796.36	$15,243.49	$14,690.61	$14,216.72	54
						47	28/6,000	EAR99	PE15A5025	$20,282.43	$19,471.13	$18,659.84	$17,848.54	55
High Power, Class AB	2 - 18	37	3.5			37	22/2,500	EAR99	PE15A5068	$17,561.50	$16,507.81	$15,629.74	$14,927.28	56
	6 - 10	43	2			43	24/7,000	EAR99	PE15A5069	$16,455.98	$15,468.62	$14,645.82	$13,987.58	57
	6 - 18	40	3			40	28/3,000	EAR99	PE15A5070	$14,949.49	$14,052.52	$13,305.05	$12,707.07	58
High Power	6.4 - 7.1	58	2			43	33/2,300	EAR99	PE15A5016	$10,021.26	$9,620.41	$9,219.56	$8,818.71	59
High Power, Class AB	8 - 12	43					28/5,000	EAR99	PE15A5071	$11,795.81	$11,088.06	$10,498.27	$10,026.44	60
		46				46	28/9,000	EAR99	PE15A5072	$18,869.81	$17,737.62	$16,794.13	$16,039.34	61

VARIABLE GAIN AMPLIFIERS

Amplifier Type	Frequency Band (GHz.)	Gain (dB)	Gain Var. ±(dB)	NF (dB)	Atten. Range (dB)	Output P1dB (dBm)	Voltage	ECCN	Model No	1	2-4	5-9	10+	ROW
Variable Gain, High Rel	100 MHz - 18	50	2	6.5	60	14	120 VAC	EAR99	PE15A7000	$18,119.27	$17,394.50	$16,669.73	$15,944.96	62
Variable Gain	500 MHz - 2	45		3.5	20	18	15 VDC	EAR99	PE15A7001	$7,084.09	$6,800.73	$6,517.36	$6,234.00	63
	500 MHz - 4	43		4				EAR99	PE15A7002	$8,270.05	$7,939.25	$7,608.45	$7,277.64	64
	1 - 18	48	3	3.5				EAR99	PE15A7009	$10,011.60	$9,611.14	$9,210.67	$8,810.21	65
	1 - 26.5	43	4	5.5		15.8		EAR99	PE15A7010	$13,475.84	$12,936.81	$12,397.77	$11,858.74	66
	1 - 40		5	5		16.5		EAR99	PE15A7011	$14,505.84	$13,925.61	$13,345.37	$12,765.14	67
	2 - 6	42	2	2		16		EAR99	PE15A7003	$8,270.05	$7,939.25	$7,608.45	$7,277.64	68
	2 - 8	43	3	2.5		15		EAR99	PE15A7004	$8,657.15	$8,310.86	$7,964.58	$7,618.29	69
	4 - 12	47		3.5		11		EAR99	PE15A7005	$8,222.84	$7,893.93	$7,565.01	$7,236.10	70
	6 - 18	45		3		17		EAR99	PE15A7006	$8,956.29	$8,598.04	$8,239.79	$7,881.54	71
	18 - 26.5			5.5		11		EAR99	PE15A7007	$11,227.00	$10,777.92	$10,328.84	$9,879.76	72
	18 - 40	48	5	5		10		EAR99	PE15A7012	$13,424.34	$12,887.37	$12,350.39	$11,813.42	73
	26.5 - 40	46	4			12.5		EAR99	PE15A7008	$12,349.70	$11,855.71	$11,361.72	$10,867.74	74

AMPLIFIER ACCESSORIES




Model No	Description	1 Pc. Price	See Web for Volume Pricing	ROW
PE15C5013	Heat Sink for Most RF Power Amplifier PE15A5000 Series	$471.61	See Web for Volume Pricing	75
PE15C5022	Heat Sink for Rf Power Amplifier PE15A5022	$633.83		76
PE15C5013F	Heat Sink with 12V Fan for Most RF Power Amplifier PE15A5000 Series	$1,352.02		77
PE15C5011F	Heat Sink with 24V Fan for RF Amplifier PE15A5011, PE15A5016, PE15A5017, PE15A5019	$1,180.50		78
PE15C5022F	Heat Sink with 24V Fan for RF Power Amplifier PE15A5022	$1,018.63		79
PE15A5990	Heat Sink with Fan for RF Power Amplifier PE15A5024, PE15A5025 and PE15A5027	$2,143.23		80
PE15C5014	Heatsink for amplifier models PE15A4011-4015 and PE15A5004-5009	$669.83		81
PE15G5060F	Heatsink for amplifier models PE15A5055-5059, PE15A5064-5065, PE15A5068 and PE15A5070	$738.77		82
PE15G5068F	Heatsink for amplifier models PE15A5060-5063, PE15A5066-5067, PE15A5069, PE15A5071-5072	$923.46		83
PE15J5011	Power and Control Cable for RF Amplifier PE15A5011, PE15A5014, PE15A5016, PE15A5017, PE15A5018, PE15A5019, PE15A5020 and PE15A5022	$242.54		84
PE15J5015	Power and Control Cable for RF Amplifier PE15A5015,PE15A5023	$128.80		85
PE15K5000	Power and Control Cable for RF Amplifier PE15B5000 and PE15B5001	$151.68		86
PE15K5002	Power and Control Cable for RF Amplifier PE15B5002	$121.29		87
PE15J000	Power and Control Cable for RF Bi-Directional Amplifier PE15B5003	$343.33		88

See Our Website For Current Pricing & Real-Time Stock Availability!

INDEX GUIDE TO
ANTENNAS

ANTENNAS 60

DIRECTIONAL ANTENNAS 60

- Dish 61
- Fixed 60
- Yagi 61
- Log 61
- Panel 60
- Sector 61

OMNI DIRECTIONAL ANTENNAS 62

- Ceiling 62
- Dome 62
- Duplexed Antenna Kits 67
- Fixed 62
- GPS Active 63
- GPS Passive 63
- Mobile 63
- Omni 64
- Panel 64
- PCB 64
- Portable 65
- Rubber Duck 66
- Vehicular 67

ANTENNA MOUNTS 67

Directional Antennas

Panel Antennas



RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
617-960 1710-2700 3300-4200 4900-6000	2:1	5.5 / 6 dBi	±45 Deg. Slant	PE51FP1012	$298.20	See Web for Volume Pricing			1
698-960 1710-2700 3400-4200	1.8:1	5 / 6 dBi	Vertical	PE51FP1013	$87.74				2
	2:1		Vertical / Horizontal	PE51239	$246.65				3
			Vertical / Horizontal	PE51FP1014	$234.91				4
824 - 960	1.8:1	9 dBi	Vertical / Horizontal	PE51FP1006	$78.02				5
902 - 928	1.2:1		LHCP	PE51025	$168.50				6
			RHCP	PE51024	$181.96				7
	1.5:1	8 dBi	LHCP	PE51FP1007	$68.61				8
			RHCP	PE51FP1008	$68.61				9
			RHCP	PE51FP1008-1	$141.92				10
			RHCP	PE51FP1008-3	$141.92				11
			RHCP	PE51FP1008-2	$141.92				12
			Vertical / Horizontal	PE51FP1005	$82.08				13
			Vertical / Horizontal	PE51FP1005-1	$77.49				14
			Vertical / Horizontal	PE51FP1005-2	$77.49				15
			Vertical / Horizontal	PE51FP1005-3	$77.49				16
			Vertical / Horizontal	PE51FP1005-4	$77.49				17
	1.8:1	9 dBi	Vertical	PE51023	$296.32				18
2,400 - 2,500 4,900 - 5,850	2:1	11 dBi	Vertical / Horizontal	PE51FP1003	$272.90				19
		14 dBi	Vertical / Horizontal	PE51FP1004	$197.32				20
		9 / 10 dBi	Vertical / Horizontal	PE51FP1002	$199.01				21
		8 / 10 dBi	Vertical / Horizontal	PE51FP1001	$52.84				22
4,900 - 5,850	1.5:1	23 dBi	Vertical / Horizontal	PE51FP1010	$122.86				23
	1.8:1	19 dBi	Vertical / Horizontal	PE51FP1011	$125.30				24
5,725 - 5,850	1.5:1		Vertical / Horizontal	PE51050	$248.03				25

Fixed Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-4	5-9	10-24	25+	ROW
4,400 - 6,400	1.5:1	9 dBi	Vertical	PE51129	$565.41	$542.79	$525.83	$514.52	26

See Our Website For Current Pricing & Real-Time Stock Availability!

Yagi Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
400 - 435 435 - 470	1.7:1	10 dBi	Linear	PE51YA1015	$140.83	See Web for Volume Pricing			27
824 - 960	1.5:1	3 dBi	Vertical / Horizontal	PE51YA1007	$41.90				28
		6 dBi	Vertical / Horizontal	PE51YA1008	$46.56				29
		9 dBi	Vertical / Horizontal	PE51YA1009	$51.58				30
		12 dBi	Vertical / Horizontal	PE51YA1010	$54.84				31
		14 dBi	Vertical / Horizontal	PE51YA1011	$65.42				32
880 - 928 928 - 960		11 / 12 dBi	Linear	PE51YA1017	$141.92				33
		13 dBi	Linear	PE51YA1016	$152.83				34
		7 / 8 dBi	Linear	PE51YA1019	$120.08				35
		9 dBi	Linear	PE51YA1018	$136.46				36
890 - 960			Vertical / Horizontal	PE51YA1012	$54.10				37
		13 dBi	Vertical / Horizontal	PE51YA1013	$81.79				38
	2.1:1	11 dBi	Vertical / Horizontal	PE51171	$383.58				39
900 - 928	1.5:1	14 dBi	Vertical / Horizontal	PE51YA1014	$178.14				40
2,400 - 2,483		12 dBi	Vertical	PE51YA1004	$68.61				41
2,400 - 2,500		9 dBi	Vertical / Horizontal	PE51YA1001	$73.66				42
		12 dBi	Vertical / Horizontal	PE51YA1002	$82.08				43
		14.5 dBi	Vertical / Horizontal	PE51YA1003	$80.99				44
4,900 - 5,850		17 dBi	Vertical / Horizontal	PE51YA1006	$222.36				45
5,725 - 5,825			Vertical	PE51YA1005	$103.31				46

Dish Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
2,400 - 2,500	1.5:1	18 dBi	H / V / 45 Deg. Slant	PE51PD1004	$171.99	$163.39	$154.79	$147.91	47
		22 dBi	H / V / 45 Deg. Slant	PE51PD1005	$205.15	$194.89	$184.64	$176.43	48
		25 dBi	H / V / 45 Deg. Slant	PE51PD1006	$370.98	$352.43	$333.88	$319.04	49
4,750 - 5,850 5,400 - 5,800		34 dBi	H / V / 45 Deg. Slant	PE51PD1003	$383.27	$364.11	$344.94	$329.61	50
		30 dBi	H / V / 45 Deg. Slant	PE51PD1002	$218.66	$207.73	$196.79	$188.05	51
4,750 - 5,850		25 dBi	H / V / 45 Deg. Slant	PE51PD1001	$185.49	$176.22	$166.94	$159.52	52

Log Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
698 - 960 1,710 - 2,500	1.6:1	10 dBi	Vertical / Horizontal	PE51LP1001	$90.96	$86.41	$81.86	$78.23	53
2,400 - 6,500	1.5:1	8 dBi	Vertical	PE51LP1002	$98.44	$93.52	$88.60	$84.66	54

Sector Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
698 - 960 1,710 - 2,700	1.6:1	14 dBi	Vertical	PE51SE1006	$408.11	$387.70	$367.30	$350.97	55
	1.8:1	12 dBi	Vertical	PE51SE1005	$392.77	$373.13	$353.49	$337.78	56
	1.9:1	9 dBi	45 Deg. Slant	PE51SE1004	$264.12	$250.91	$237.71	$227.14	57
900 - 930	2:1	13 dBi	Horizontal	PE51SE1003	$313.25	$297.59	$281.93	$269.40	58
902 - 928	1.5:1		Vertical / Horizontal	PE51FP1009	$435.57	$413.79	$392.01	$374.59	59
2,400 - 2,500	1.3:1	2 dBi	Vertical	PE51SE1009	$528.22	$501.81	$475.40	$454.27	60
	1.5:1	14 dBi	Vertical / Horizontal	PE51SE1001	$254.30	$241.59	$228.87	$218.70	61

See Our Website For Current Pricing & Real-Time Stock Availability!

Sector Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
2,400 - 2,500 4,900 - 5,850	1.5/2:1	13 / 15 dBi	Vertical / Horizontal	PE51SE1002	$493.11	$468.45	$443.80	$424.07	62
4,900 - 5,850	1.7:1	16 dBi	Vertical / Horizontal	PE51SE1008	$147.43	$140.06	$132.69	$126.79	63
2,400 - 2,500 5,725 - 5,875	1.5:1	5 dBi	Vertical / Horizontal	PE51SE1007	$67.19	$63.83	$60.47	$57.78	64

Omni Directional Antennas

Ceiling Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
617 - 960 1350 - 2700 3300 - 3800 4900 - 6000	1.8:1	1.5 / 3.5 dBi	Linear	PE51217	$102.71	$97.57	$92.44	$88.33	65
			Linear	PE51223	$107.85	$102.46	$97.07	$92.75	66
			Linear / Horizontal	PE51218	$189.61	$180.13	$170.65	$163.06	67
			Linear / Horizontal	PE51224	$199.09	$189.14	$179.18	$171.22	68
617 - 960 1710 - 2700 3400 - 4200 4900 - 6000		1.8 / 2 dBi	vertical	PE51219	$102.97	$97.82	$92.67	$88.55	69
			vertical	PE51225	$106.62	$101.29	$95.96	$91.69	70
698 - 960 1350 - 2700 3300 - 4200		2.2 / 3.5 dBi	Linear	PE51220	$71.67	$68.09	$64.50	$61.64	71
			Linear	PE51226	$75.26	$71.50	$67.73	$64.72	72
	2:1	1.5 / 2.2 dBi	Linear / Horizontal	PE51221	$95.07	$90.32	$85.56	$81.76	73
			Linear / Horizontal	PE51227	$99.82	$94.83	$89.84	$85.85	74
698 - 960 1710 - 2700		3 / 3.5 dBi	Vertical / Horizontal	PE51222	$96.50	$91.68	$86.85	$82.99	75
			Vertical / Horizontal	PE51228	$101.33	$96.26	$91.20	$87.14	76

Dome Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
698 - 960 1,710 - 2,700	1.7:1	2 / 5 dBi	Vertical	PE51158	$39.27		See Web for Volume Pricing		77
800 - 3,000	2:1	3 dBi	Vertical	PE51059	$444.57				78
		7.5 dBi	Vertical	PE51058	$357.31				79
806 - 960 1,710 - 2,500	1.5:1	3 dBi	Vertical	PE51096	$52.77				80

Fixed Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
902 - 928	2:1	5 dBi	Vertical	PE51028	$242.78		See Web for Volume Pricing		81
2,250 - 2,350	1.43:1	3 dB	Vertical	PE51062	$142.75				82
2,350 - 2,450	1.3:1	3 dBi	Vertical	PE51063	$307.74				83
2,400 - 2,500	2.1:1	8 dBi	Vertical	PE51172	$176.57				84
	2:1		Vertical	PE51061	$283.77				85
2,450 - 2,550	1.43:1	3 dB	Vertical	PE51064	$169.23				86
3,400 - 3,600	1.5:1	11 dBi	Vertical	PE51034	$111.77				87
3,450 - 3,550	1.4:1	3 dBi	Vertical	PE51065	$145.47				88

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
5,470 - 5,725	1.5:1	12 dBi	Vertical	PE51037	$89.02	$84.57	$80.12	$76.56	89
5,725 - 5,850			Vertical	PE51040	$126.56	$120.23	$113.90	$108.84	90

GPS Active Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
824 - 2,170	2.5:1	5 dBic		PE51212	$13.50		See Web for Volume Pricing		91
1,570 - 1,580	1.3:1	32 dBiC	RHCP	PE51067	$411.16				92
1,574 - 1,610	2:1	32 dBi	RHCP	PE51TM1000	$174.10				93

GPS Passive Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
1,220 - 1,230 1,530 - 1,580	2:1	6 dBic	RHCP	PE51068	$1,139.45		See Web for Volume Pricing		94
1,572.42 - 1,578.42	1.5:1	3 dBi	RHCP	PE51066-1	$140.18				95
			RHCP	PE51066-2	$108.25				96
1,574 - 1,610	2:1	32 dBi		PE51TM1001	$208.80				97
1,575 - 1,615		3 dB	RHCP	PE51GPS1004	$32.05				98

Mobile Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
824 - 960 1,710 - 2,200 2,400 - 2,500	2:1	2 / 2 dBi	Vertical	PE51GM1002	$27.94	$25.98	$24.03	$22.35	99
880 - 965 1,710 - 2,170		3 dBi	Vertical	PE51113-1	$55.25	$52.49	$49.73	$47.52	1
			Vertical	PE51113-2	$61.15	$58.09	$55.04	$52.59	2
			Vertical	PE51113-3	$48.43	$46.01	$43.59	$41.65	3
			Vertical	PE51113-4	$50.44	$47.92	$45.40	$43.38	4
900 - 960 2,400 - 2,500	1.5:1		Vertical	PE51MO1001	$77.99	$74.09	$70.19	$67.07	5
		3 / 3 dBi	Vertical	PE51MO1002	$70.78	$67.24	$63.70	$60.87	6
900 - 960 2,400 - 2,500		3 dBi	Vertical	PE51OM1022	$101.68	$96.60	$91.51	$87.44	7
902 - 928	2:1	4 dBi	Vertical	PE51027	$45.69	$43.41	$41.12	$39.29	8
2,400 - 2,500	1.5:1	3 dBi	Vertical	PE51MO1003	$98.93	$93.98	$89.04	$85.08	9
			Vertical	PE51OM1023	$95.90	$91.11	$86.31	$82.47	10
		5 dBi	Vertical	PE51MO1004	$73.17	$69.51	$65.85	$62.93	11
		3 dB	Vertical	PE51136	$123.50	$117.33	$111.15	$106.21	12

See Our Website For Current Pricing & Real-Time Stock Availability!

Omni Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
698 - 960 1,710 - 2,700	1.6:1	4 dBi	Vertical	PE51OM1020	$61.65	$58.57	$55.49	$53.02	13
824 - 928 900 - 928	1.7:1	8.5 / 10 dBi	Vertical / Horizontal	PE51OM1021	$818.72	$777.78	$736.85	$704.10	14
824 - 960	1.5:1	6 dBi	Vertical	PE51OM1014	$82.67	$78.54	$74.40	$71.10	15
		3 / 6 dBi	Vertical	PE51OM1013	$74.76	$71.02	$67.28	$64.29	16
900 - 928		6 dBi	Vertical	PE51OM1015	$125.32	$119.05	$112.79	$107.78	17
		8 dBi	Vertical	PE51OM1016	$182.50	$173.38	$164.25	$156.95	18
	1.6:1		Vertical	PE51OM1019	$128.89	$122.45	$116.00	$110.85	19
		3 / 6 dBi	Vertical	PE51OM1017	$77.99	$74.09	$70.19	$67.07	20
		6 / 6 dBi	Vertical	PE51OM1018	$95.98	$91.18	$86.38	$82.54	21
2,400 - 2,500	1.5:1	4 dBi	Vertical	PE51OM1024	$97.18	$92.32	$87.46	$83.57	22
	2:1	7.4 dBi	Vertical	PE51OM1025	$124.11	$117.90	$111.70	$106.73	23
		8 dBi	Vertical	PE51OM1026	$92.10	$87.50	$82.89	$79.21	24
2,400 - 2,500 5,100 - 5,800	1.6:1	6 dBi	Vertical / Horizontal	PE51OM1009	$252.92	$240.27	$227.63	$217.51	25
		6 / 11 dBi	Vertical / Horizontal	PE51OM1008	$368.53	$350.10	$331.68	$316.94	26
		6 / 6 dBi	Vertical / Horizontal	PE51OM1010	$313.13	$297.47	$281.82	$269.29	27
		6 / 9 dBi	Vertical / Horizontal	PE51OM1007	$307.10	$291.75	$276.39	$264.11	28
	1.6/1.9:1	6 / 11 dBi	Vertical / Horizontal	PE51OM1011	$388.28	$368.87	$349.45	$333.92	29
2,400 - 2,500 5,725 - 5,850	1.5:1	6 / 6 dBi	Vertical	PE51OM1004	$135.14	$128.38	$121.63	$116.22	30
	1.6:1	9 / 9 dBi	Vertical	PE51OM1005	$147.43	$140.06	$132.69	$126.79	31
2,400 - 2,500 4,900 - 5,850	1.8:1	4 / 6 dBi	Vertical	PE51OM1012	$165.85	$157.56	$149.27	$142.63	32
	2.5:1	5 / 6 dBi	Vertical	PE51OM1002	$59.83	$56.84	$53.85	$51.45	33
		7 / 8 dBi	Vertical	PE51OM1003	$69.78	$66.29	$62.80	$60.01	34
	2:1	3.5 / 4 dBi	Vertical	PE51OM1001	$51.58	$49.00	$46.42	$44.36	35
2,400 - 2,500 5,100 - 5,900	1.8:1	6 / 6 dBi	Vertical / Horizontal	PE51OM1006	$245.69	$233.41	$221.12	$211.29	36
698 - 806 806 - 960		3 / 3 dBi	Vertical	PE51OM1031	$69.42	$65.95	$62.48	$59.70	37
			Vertical	PE51OM1032	$72.88	$69.24	$65.59	$62.68	38

Panel Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
617 - 698 698 - 960 1,710 - 2,700 3,400 - 4,200 4,900 - 6,000	2:1	5.5 / 6 dBi	±45 Deg. Slant	PE51FP1015	$313.11	$297.45	$281.80	$269.27	39
698 - 806 806 - 960 1,710 - 2,700 2,200 - 2,700 3,400 - 4,200	1.8:1	5 / 6 dBi	Vertical	PE51FP1016	$92.13	$87.52	$82.92	$79.23	40

PCB Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
698 - 960 1,710 - 2,170 2,300 - 2,700	2.5:1	5 / 3 dBi	Vertical	PE51200	$6.49	$6.23	$6.04	$5.91	41
704 - 960 1,574 - 1,576 1,710 - 2,200 2,496 - 2,690	2:1	3 dBi		PE51199	$7.31	$7.02	$6.80	$6.65	42

See Our Website For Current Pricing & Real-Time Stock Availability!

PCB Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
824 - 960	3:1	0 dBi	Vertical	PE51195	$9.35	$8.98	$8.70	$8.51	43
824 - 960 1,710 - 2,200	2.5:1			PE51198	$7.31	$7.02	$6.80	$6.65	44
	2:1	2 dBi		PE51197	$16.02	$15.38	$14.90	$14.58	45
	3:1	3 dBi	Vertical	PE51196	$9.35	$8.98	$8.70	$8.51	46
824 - 960 1,710 - 1,880 1,900 - 2,200		0 dBi		PE51194	$9.35	$8.98	$8.70	$8.51	47
860 - 960		2 dBi	Vertical	PE51216	$13.92	$13.36	$12.95	$12.67	48
2,400 - 2,500	2.3:1		Vertical / Horizontal	PE51213	$14.04	$13.48	$13.06	$12.78	49
	2:1	1 dBi		PE51206	$5.56	$5.34	$5.17	$5.06	50
		2 dBi		PE51204	$4.39	$4.21	$4.08	$3.99	51
				PE51208	$5.56	$5.34	$5.17	$5.06	52
		2.6 dBi	Vertical	PE51209	$9.30	$8.93	$8.65	$8.46	53
				PE51205	$4.39	$4.21	$4.08	$3.99	54
				PE51207	$5.56	$5.34	$5.17	$5.06	55
		3.5 dBi	Vertical	PE51210	$9.30	$8.93	$8.65	$8.46	56
2,400 - 2,500 4,900 - 5,900	2.5:1	4.5 / 4.5 dBi	DHCP	PE51203	$6.96	$6.68	$6.47	$6.33	57
	2:1	2.5 dBi		PE51201	$6.73	$6.46	$6.26	$6.12	58
				PE51202	$6.96	$6.68	$6.47	$6.33	59
2,400 - 2,500 5,100 - 5,900		3 / 6 dBi	Vertical / Horizontal	PE51214	$17.99	$17.27	$16.73	$16.37	60
4,900 - 5,900		4.5 dBi	Horizontal	PE51215	$16.70	$16.03	$15.53	$15.20	61
5,150 - 5,850	2:1	3 dBi		PE51211	$4.62	$4.44	$4.30	$4.20	62

Portable Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
118 - 174	2:1	0 dBi	Vertical	PE51TW1000	$34.61	$32.19	$29.76	$27.69	63
400 - 420			Vertical	PE51146	$23.50	$22.33	$21.15	$20.21	64
420 - 450			Vertical	PE51159	$27.64	$26.26	$24.88	$23.77	65
			Vertical	PE51160	$18.14	$17.23	$16.33	$15.60	66
470 - 512			Vertical	PE51161	$22.17	$21.06	$19.95	$19.07	67
615 - 960 1,710 - 2,690	3:1	3 dBi	Vertical	PE51OM1030	$75.60	$70.31	$65.02	$60.48	68
615 - 960 1,710 - 2,700		3.5 / 3.5 dBi	Vertical	PE51OM1027	$75.60	$70.31	$65.02	$60.48	69
			Vertical	PE51OM1029	$75.60	$70.31	$65.02	$60.48	70
615 - 960 1,400 - 2,700 3,300 - 4,200		4.5 / 4.5 dBi	Vertical	PE51RD1031	$22.35	$20.79	$19.22	$17.88	71
615 - 960 1,710 - 2,700 3,300 - 4,200 5,150 - 7,150		3.5 / 2 dBi	Vertical	PE51RD1030	$31.32	$29.13	$26.94	$25.06	72
617 - 960 1,710 - 2,690		3 dBi	Vertical	PE51OM1028	$75.60	$70.31	$65.02	$60.48	73
617 - 960 1,427 - 2,700 3,300 - 5,580	3.5:1	2 dBi	Vertical	PE51RD1032	$26.82	$24.94	$23.07	$21.46	74
698 - 780	2:1	0 dBi	Vertical	PE51157	$20.99	$19.94	$18.89	$18.05	75
698 - 870	2.3:1	2 dBi	Vertical	PE51154	$27.31	$25.94	$24.58	$23.49	76
	2:1		Vertical	PE51152	$22.79	$21.65	$20.51	$19.60	77
698 - 960 1,710 - 2,700	4.5:1	3 dBi	Vertical	PE51RD1027	$16.80	$15.62	$14.45	$13.44	78
700 - 960 1,710 - 2,170 2,500 - 2,700	2.5:1	4 dBi	Vertical	PE51RD1028	$16.80	$15.62	$14.45	$13.44	79
760 - 870	2:1	0 dBi	Vertical	PE51166	$25.66	$24.38	$23.09	$22.07	80
880 - 960			Vertical	PE51164	$17.67	$16.79	$15.90	$15.20	81
			Vertical	PE51165	$21.92	$20.82	$19.73	$18.85	82
890 - 960 1,710 - 1,880		3 dBi	Vertical	PE51089-1	$48.02	$45.62	$43.22	$41.30	83
			Vertical	PE51089-2	$41.60	$39.52	$37.44	$35.78	84
			Vertical	PE51089-3	$39.53	$37.55	$35.58	$34.00	85
			Vertical	PE51089-4	$39.78	$37.79	$35.80	$34.21	86

See Our Website For Current Pricing & Real-Time Stock Availability!

Portable Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
900 - 960	1.5:1	0 dBi	Vertical	PE51056	$51.86				87
	2.1:1	3 dBi	Vertical	PE51055	$102.92				88
902 - 928	2:1		Vertical	PE51026	$26.39				89
1,700 - 1,850		3.5 dBi	Vertical	PE51119	$567.22				90
1,700 - 2,500		2 dBi	Vertical	PE51117A	$771.37				91
			Vertical	PE51173	$473.34				92
1,900 - 2,500		3.5 dBi	Vertical	PE51121	$733.73				93
2,200 - 2,500		6 dBi	Vertical	PE51123	$747.60				94
2,300 - 2,700		6.5 dBi	Vertical	PE51090	$18.46				95
2,400 - 2,500	1.43:1	3 dBi	Vertical	PE51133	$197.61				96
	2:1	2.2 dBi	Vertical / Horizontal	PE51077	$39.71				97
		5.5 dBi	Vertical	PE51078	$23.98				98
2,400 - 2,500 4,900 - 5,800	2.5:1	2 dBi	Vertical	PE51088	$39.71	See Web for Volume Pricing			99
	2:1	2.5 dBi	Vertical	PE51087	$29.71				1
2,400 - 2,500 4,900 - 5,825		2 dBi	Vertical	PE51080	$34.45				2
			Vertical	PE51082	$26.06				3
			Vertical	PE51083	$21.84				4
		2 / 3 dBi	Vertical	PE51081	$26.67				5
2,400 - 2,500 5,000 - 5,900		3.5 / 6 dBi	Vertical	PE51142	$31.21				6
			Vertical	PE51143	$20.57				7
			Vertical	PE51144	$19.41				8
2,400 - 7,125	1.7:1	3 dBi	Vertical	PE51RD1025	$25.54				9
			Vertical	PE51RD1026	$25.54				10
3,300 - 3,800	2:1	2 dBi	Vertical	PE51084	$37.46				11
3,400 - 3,800		5 dBi	Vertical	PE51085	$21.28				12
4,400 - 5,000		6 dBi	Vertical	PE51135A	$579.76				13
			Vertical	PE51134	$911.91				14
5,250 - 5,850		3.8 dBi	Vertical	PE51125A	$573.13				15
		6 dBi	Vertical	PE51127	$601.29				16

Rubber Duck Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
860 - 960	2:1	3 dBi	Vertical	PE51RD1008	$24.12	$22.43	$20.74	$19.30	17
			Vertical	PE51RD1009	$24.12	$22.43	$20.74	$19.30	18
900 - 930	2.5:1	5 dBi	Vertical	PE51RD1019	$33.00	$30.69	$28.38	$26.40	19
			Vertical	PE51RD1010	$33.00	$30.69	$28.38	$26.40	20
			Vertical	PE51RD1011	$33.00	$30.69	$28.38	$26.40	21
			Vertical	PE51RD1012	$33.00	$30.69	$28.38	$26.40	22
	2:1		Linear	PE51RD1018	$20.10	$18.69	$17.29	$16.08	23
2,400 - 2,500		2 dBi	Linear	PE51RD1020	$10.08	$9.37	$8.67	$8.06	24
			Linear	PE51RD1022	$8.19	$7.62	$7.04	$6.55	25
		3 dBi	Linear	PE51RD1013	$5.85	$5.44	$5.03	$4.68	26
			Linear	PE51RD1023	$5.85	$5.44	$5.03	$4.68	27
			Linear	PE51RD1024	$8.19	$7.62	$7.04	$6.55	28
		4.52 dBi	Linear	PE51RD1014	$15.98	$14.86	$13.74	$12.78	29
			Linear	PE51RD1015	$11.48	$10.68	$9.87	$9.18	30
			Linear	PE51RD1016	$15.98	$14.86	$13.74	$12.78	31
		5.5 dBi	Vertical	PE51RD1007	$15.67	$14.89	$14.10	$13.48	32
		7 dBi	Linear	PE51RD1017	$14.93	$13.88	$12.84	$11.94	33
2,400 - 2,500 4,900 - 5,350 5,725 - 5,850		3 / 3 dBi	Vertical	PE51RD1001	$21.97	$20.87	$19.77	$18.89	34
			Vertical	PE51RD1002	$21.35	$20.28	$19.22	$18.36	35
			Vertical	PE51RD1003	$21.97	$20.87	$19.77	$18.89	36
			Vertical	PE51RD1004	$21.54	$20.46	$19.39	$18.52	37
2,400 - 2,500 5,150 - 5,850		4.5 / 7 dBi	Vertical	PE51RD1006	$33.96	$32.26	$30.56	$29.21	38
2,400 - 2,483 5,100 - 5,900		3 / 5 dBi	Vertical	PE51RD1005	$27.15	$25.79	$24.44	$23.35	39
2,400 - 2,500		2 dBi	Linear	PE51RD1021	$4.68	$4.35	$4.02	$3.74	40

See Our Website For Current Pricing & Real-Time Stock Availability!

Vehicular Antennas

RF Frequency Range (MHz)	VSWR	Gain Nominal	Polarization	Model No	1-24	25-49	50-99	100+	ROW
108 - 520	2:1	2 dBi	Linear, Vertical	PE51MP1000	$60.03	$55.83	$51.63	$48.02	41
132 - 174	1.5:1	3 dB	Linear, Vertical	PE51MP1001	$73.53	$68.38	$63.24	$58.82	42
	2:1	2 dBi	Linear, Vertical	PE51MP1002	$80.40	$74.77	$69.14	$64.32	43
144 - 174	1.5:1	3 dB	Linear, Vertical	PE51MP1004	$73.53	$68.38	$63.24	$58.82	44
	2:1	2 dBi	Linear, Vertical	PE51MP1003	$107.17	$99.67	$92.17	$85.74	45
			Linear, Vertical	PE51MP1009	$80.40	$74.77	$69.14	$64.32	46
380 - 520			Linear, Vertical	PE51MP1005	$73.80	$68.63	$63.47	$59.04	47
420 - 470	1.5:1	3 dB	Linear, Vertical	PE51MP1006	$67.96	$63.20	$58.45	$54.37	48
		5 dB	Linear, Vertical	PE51MP1007	$77.91	$72.46	$67.00	$62.33	49
440 - 480	2:1	3 dBd	Linear, Vertical	PE51MP1008	$83.31	$77.48	$71.65	$66.65	50
450 - 520 746 - 960		2 dBi	Linear, Vertical	PE51MP1011	$64.70	$60.17	$55.64	$51.76	51
698 - 960 1,710 - 2,150 2,150 - 2,700		2 / 3 dBi	Linear, Vertical	PE51MP1010	$59.40	$55.24	$51.08	$47.52	52
824 - 960 1,710 - 1,990		2 dBi	Vertical	PE51GM1001	$20.53	$19.09	$17.66	$16.42	53

Duplexed Antenna Kits

RF Frequency Range (MHz)	VSWR	Contains	Model No	1-24	25-49	50-99	100+	ROW
100 - 180 380 - 520	1.6:1	Duplexer (VHF/UHF 108-174 MHz/380-870 MHz), with integral N-type (m) Connectors (3 ea.); Low Loss 195 NMO mount with cable (1 ea.); RG-58/U NMO mount with cable (1 ea.); Field Tunable Antennas (2 ea.)//RG-58/U Feed Cable (1 ea.)	PE51AK1000	$272.80	$253.70	$234.61	$218.24	54
		Duplexer (VHF/UHF 108-174MHz/380-870MHz) with integral N-Type (m) Connectors (3 ea.); Low Loss PE51GPS1000 NMO Combination mount with integrated GPS antenna (1 ea.); RG-58/U NMO mount (1 ea.); Field Tunable Antennas (2 ea.); RG-58/U Feed Vable (1 ea.); PE51GPS1000 NMO Combination mount with integrated GPS antenna	PE51AK1001	$348.99	$324.56	$300.13	$279.19	55
		Duplexer (VHF/UHF 108-174MHz/450-520MHz/746-870MHz) with integral N-Type (m) Connectors (3 ea.); Low Loss PE51GPS1000 NMO Combination mount with integrated GPS antenna (1 ea.); RG-58/U NMO mount (1 ea.); PE51MP1011 multiband antenna (1 ea.); PE51MP1000 tunable VHF/UHF antenna (1 ea.)//RG-58/U Feed Cable (1 ea.)	PE51AK1002	$454.67	$422.84	$391.02	$363.74	56
		Duplexer (VHF/UHF 108-174MHz/450-520MHz/746-870MHz) with integral N-type (m) Connectors (3 ea.); Low loss 195 NMO mount (1 ea.); RG-58/U NMO mount (1 ea.); PE51MP1011 multiband antenna (1 ea.); PE51MP1000 tunable VHF/UHF antenna (1 ea.); RG-58/U Feed Cable (1 ea.)	PE51AK1003	$360.46	$335.23	$310.00	$288.37	57

Antenna Mounts

RF Frequency Range (MHz)	VSWR	Gain Nominal	Description	Model No	1-24	25-49	50-99	100+	ROW
1,166 - 1,606		43 dBi	Multi Band 43dBi Timing GPS/GLNSS Antenna 1,166-1,606 MHz N Type Female Connector	PE51GPS1005	Call	Call	Call	Call	58
1,575 - 1,615	2:1	28 dB	NMO Mount Combo 28 dB GPS Vehicular Antenna NMO Mount/SMA Connectors RG58 cable	PE51GPS1002	$135.17	$125.71	$116.25	$108.14	59
			NMO Mount Combo 28 dB GPS Vehicular Antenna NMO Mount/SMA Connectors LL195 cable	PE51GPS1003	$153.61	$142.86	$132.10	$122.89	60
N/A			Base Station Antenna Ground Plane Converter Kit NMO Mount/N Type Connectors	PE51AK1004	$50.31	$46.79	$43.27	$40.25	61
1,575 - 1,615	2:1	30 dB	NMO Mount Combo 30 dB GPS/GLNSS Vehicular Antenna NMO Mount/SMA Connectors RG58 cable	PE51GPS1000	$135.17	$125.71	$116.25	$108.14	62
			NMO Mount Combo 30 dB GPS Vehicular Antenna NMO Mount/SMA Connectors LL195 cable	PE51GPS1001	$153.61	$142.86	$132.10	$122.89	63

See Our Website For Current Pricing & Real-Time Stock Availability!

Attenuators and Equalizers Selection Guide

3 Easy Ways to Find your Product.....

1. Search by PE Part Number

If you know the PE part number you are searching for, please reference our Part Number Index on Page 395.

2. Quick Reference Guide

Attenuators 68
- **CMOS, Relay, TTL and USB Controlled Attenuators** 85
- **Continuously Variable Attenuators**
  - 50 Ohm 85
- **DC Bias Attenuators**
  - 50 Ohm 84
  - 75 Ohm 84
- **Fixed Attenuators**
  - 50 Ohm 70
  - 75 Ohm 82
- **Step Attenuators, Push Button**
  - 50 Ohm 83
  - 75 Ohm 83
- **Step Attenuators, Rotary**
  - 50 Ohm 84
  - 75 Ohm 84
- **Step Attenuators, Toggle**
  - 75 Ohm 83
- **Voltage Variable Attenuators** 85

Equalizers 86

3. Attenuators Locator

Connector In-Out	Max Freq.	Power	Model No.	Page
1.85mm Male				
1.85mm Female	65 GHz	1 W	PE7403	70
2.4mm Female				
2.4mm Female	40 GHz	0.25 W	PE70A6001	85
2.4mm Male				
2.4mm Female	50 GHz	1 W	PE7089	70
2.92mm Female				
2.92mm Female	18 GHz	0.25 W	PE70A5001	85
	40 GHz	0.1 W	PE70A3901	
		0.25 W	PE70A5002	
2.92mm Male				
2.92mm Female	26.5 GHz	2 W	PE7024	71
			PE7024/SP	
	40 GHz	0.5 W	PE7AP412	70
			PE7046	
			PE7AP412	
		1 W	PE7088	
		2 W	PE7090	71
			PE7395	72
		10 W	PE7AP402	75
4.3-10 Male				
4.3-10 Female	6 GHz	15 W	PE7AP1001	76
7/16 DIN Female				
7/16 DIN Female	6 GHz	25 W	PE7380	76
		50 W	PE7313	77
		100 W	PE7204	79
	7.5 GHz	25 W	PE7380	76
		50 W	PE7313	77
				78

Connector In-Out	Max Freq.	Power	Model No.	Page
7/16 DIN Female				
7/16 DIN Male	6 GHz	50 W	PE7310	77
		100 W	PE7201	79
	7.5 GHz	50 W	PE7310	77
N Female	6 GHz	50 W	PE7316	78
			PE7321	
		100 W	PE7212	80
	7.5 GHz	50 W	PE7316	78
	18 GHz		PE7321	
N Male	6 GHz	100 W	PE7207	80
7/16 DIN Male				
7/16 DIN Female	6 GHz	25 W	PE7379	76
		50 W	PE7312	77
		100 W	PE7203	79
	7.5 GHz	5 W	PE7039	74
		10 W	PE7040	75
		25 W	PE7041	76
			PE7379	
		50 W	PE7042	77
			PE7312	
N Female	6 GHz	100 W	PE7211	79
BNC Female				
BNC Female	0.5 GHz	1 W	PE7008	83
			PE7035	84
	0.75 GHz		PE7008	83
			PE70A1021	
			PE7008	
			PE70A1001	
	1 GHz		PE7034	84
			PE7035	
	2GHz	2 W	PE7034	
	2.2 GHz		PE70A1024	
			PE70A1022	

Attenuators Locator

Connector In-Out	Max Freq.	Power	Model No.	Page
BNC Male				
BNC Female	1 GHz	1 W	PE7009	82
		100 W	PE7026	80
	2 GHz	1 W	PE7000	70
		10 W	PE7025	75
	4 GHz	2 W	PE7049	72
			PE7050	82
F Female				
F Female	1 GHz	1 W	PE70A8003	85
			PE70A8004	
			PE70A1008	83
	2.15 GHz	0 W	PE70A5011	85
		30 W	PE70A5012	
F Male				
F Female	1 GHz	2 W	PE7057	82
	2 GHz		PE7064	84
	3 GHz		PE7396	82
N Female				
7/16 DIN Female	6 GHz	25 W	PE7369	77
		50 W	PE7315	78
		100 W	PE7206	81
	7.5 GHz	25 W	PE7369	77
		50 W	PE7315	78
7/16 DIN Male	6 GHz	25 W	PE7370	76
		50 W	PE7311	78
		100 W	PE7202	80
				81
	7.5 GHz	25 W	PE7370	76
				77
		50 W	PE7311	78
N Female	6 GHz	50 W	PE7323	79
		100 W	PE7214	81
	8 GHz	25 W	PE7371	77
	18 GHz			
		50 W	PE7323	79
N Male	6 GHz	50 W	PE7317	79
		100 W	PE7208	81
	18 GHz	50 W	PE7317	79
TNC Female	18 GHz	25 W	PE7372	77
N Male				
7/16 DIN Female	6 GHz	25 W	PE7366	76
		50 W	PE7314	78
		100 W	PE7205	80
	7.5 GHz	25 W	PE7366	76
		50 W	PE7314	78
N Female	1 GHz	1 W	PE7029	82
		300 W	PE7031	
		500 W	PE7032	
	1.5 GHz	100 W	PE7021	80
	2 GHz	2 W	PE7062	84
		10 W	PE7010	75
	2.4 GHz	500 W	PE7085	82
	2.5 GHz	1000 W	PE7423	
	3 GHz	1 W	PE7002	71
		5 W	PE7390	74
		10 W	PE7386	75
		50 W	PE7388	78
			PE7389	
		100 W	PE7385	80
		200 W	PE7387	81
		500 W	PE7AP418	82
	4 GHz	2 W	PE7044	
		25 W	PE7392	76
		50 W	PE7394	78
		100 W	PE7421	80
	6 GHz	5 W	PE7AP006	74
		50 W	PE7322	78
		100 W	PE7213	80
	8 GHz	25 W	PE7367	76
		150 W	PE7AP150	81
	8.5 GHz	250 W	PE7AP250	82
	12.4 GHz	10 W	PE7048	75
	18 GHz	2 W	PE7004	72
			PE7047	
		5 W	PE7014	74
		10 W	PE7015	75
		25 W	PE7017	76
			PE7426	
			PE7367	
		50 W	PE7019	78
			PE7322	
		100 W	PE7424	80
		200 W	PE7AP200	82
TNC Female	6 GHz	100 W	PE7237	80
QMA Male				
QMA Female	6 GHz	1 W	PE7AP1002	71

Connector In-Out	Max Freq.	Power	Model No.	Page
QN Male				
QN Female	3 GHz	1 W	PE7AP1000	71
SMA Female				
SMA Female	1 GHz	0.5 W	PE70A8000	85
		1 W	PE70A8001	
	1.5 GHz		PE70A8005	
	2 GHz	0.5 W	PE70A8002	
	2.2 GHz	2 W	PE70A1025	84
			PE70A1023	
		10 W	PE70A1031	85
	3 GHz	0 W	PE70A5004	
			PE70A5006	
			PE70A5005	
			PE70A5007	
			PE70A5008	
	4 GHz		PE70A2000	
		5 W	PE7422	85
	6 GHz	0 W	PE70A1000	85
			PE70A5009	
			PE70A5013	
			PE70A5010	
			PE70A3902	
		0.1 W	PE70A5000	
		100 W	PE7228	81
	8 GHz	0 W	PE70A2001	85
	12 GHz		PE70A2002	
	13 GHz	0.16 W	PE70A4000	
		0.32 W	PE70A5003	85
	18 GHz	0 W	PE70A2003	86
		0.1 W	PE70A3900	
		1 W	PE70A6000	
		20 W	PE70A2900	
		25 W	PE7363	77
		50 W	PE7337	79
	20 GHz	18 W	PE70A1017	85
SMA Male	6 GHz	100 W	PE7221	81
SMA Male				
SMA Female	1.5 GHz	100 W	PE7022	81
	2 GHz	1 W	PE7161	71
		2 W	PE7061	84
	3 GHz		PE7001	72
		5 W	PE7391	74
	4 GHz	25 W	PE7393	77
	6 GHz	2 W	PE70A1009	72
			PE70A1010	
			PE70A1011	
			PE70A1012	
			PE70A1014	
			PE70A1015	
			PE7091	73
			PE7162	
		10 W	PE7428	75
		25 W	PE7357	77
		100 W	PE7227	81
	12.4 GHz	2 W	PE7045	73
	18 GHz		PE7005	
			PE7092	
		5 W	PE7013	75
		10 W	PE7016	
				76
		25 W	PE7018	77
			PE7357	
		50 W	PE7020	79
			PE7427	
		100 W	PE7425	81
	26 GHz	2 W	PE7087	73
				74
TNC Female				
N Female	6 GHz	100 W	PE7218	81
N Male	6 GHz	100 W	PE7210	81
TNC Female	18 GHz	50 W	PE7351	79
TNC Male				
TNC Female	1.5 GHz	100 W	PE7056	81
	2 GHz	1 W	PE7003	71
				74
		2 W	PE7063	84
	12.4 GHz		PE7051	74
	18 GHz		PE7030	
		5 W	PE7052	75
		10 W	PE7053	76
		25 W	PE7054	77
			PE7375	
		50 W	PE7055	79

PASSIVE ATTENUATORS

Fixed Attenuators

50 Ohm

Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
0.5 W	2.92mm Male	2.92mm Female	40 GHz	Passivated Stainless Steel	1.4:1		0	PE7AP412-00	$253.32	See Web for Volume Pricing			1
							1	PE7AP412-01	$253.12				
							2	PE7AP412-02	$253.12				
							3	PE7AP412-03	$252.23				
						Yes	3	PE7046-3	$504.51				2
						Yes	6	PE7046-6	$504.51				
						Yes	10	PE7046-10	$488.43				
						Yes	20	PE7046-20	$497.06				
						Yes	30	PE7046-30	$504.51				
							4	PE7AP412-04	$274.04				3
							5	PE7AP412-05	$263.77				
							6	PE7AP412-06	$268.53				
							8	PE7AP412-08	$278.86				
							9	PE7AP412-09	$264.42				
					1.5:1		10	PE7AP412-10	$274.04				
							12	PE7AP412-12	$259.87				
							15	PE7AP412-15	$259.87				
							20	PE7AP412-20	$274.04				
							30	PE7AP412-30	$273.14				
1 W	1.85mm Male	1.85mm Female	65 GHz	Passivated Stainless Steel	1.65:1		1	PE7403-1	$758.96				4
							2	PE7403-2	$758.96				
							3-3	PE7403-3	$662.31				
							4	PE7403-4	$719.68				
							5	PE7403-5	$730.46				
							6-6	PE7403-6	$650.47				
							7	PE7403-7	$719.68				
							8	PE7403-8	$719.68				
							9	PE7403-9	$719.68				
							10-10	PE7403-10	$652.53				
							20-20	PE7403-20	$662.60				
							30-30	PE7403-30	$684.54				
	2.4mm Male	2.4mm Female	50 GHz		1.75:1	Yes	10	PE7089-10	$411.39				5
						Yes	12	PE7089-12	$411.39				
						Yes	15	PE7089-15	$411.39				
						Yes	20	PE7089-20	$411.19				
						Yes	30	PE7089-30	$410.27				
						Yes	0	PE7089-0	$390.10				
						Yes	1	PE7089-1	$411.39				
						Yes	2	PE7089-2	$411.39				
						Yes	3	PE7089-3	$399.76				
						Yes	4	PE7089-4	$390.10				
						Yes	5	PE7089-5	$395.94				
						Yes	6	PE7089-6	$405.47				
						Yes	7	PE7089-7	$390.10				
						Yes	8	PE7089-8	$411.39				
						Yes	9	PE7089-9	$395.94				
	2.92mm Male	2.92mm Female	40 GHz		1.4:1	Yes	0	PE7088-0	$352.53				6
						Yes	1	PE7088-1	$336.52				
						Yes	2	PE7088-2	$336.52				
						Yes	3	PE7088-3	$309.00				
						Yes	4	PE7088-4	$352.53				
						Yes	5	PE7088-5	$352.53				
						Yes	6	PE7088-6	$308.78				
						Yes	7	PE7088-7	$352.53				
						Yes	8	PE7088-8	$352.53				
						Yes	9	PE7088-9	$347.33				
						Yes	10	PE7088-10	$315.94				
						Yes	12	PE7088-12	$352.53				
						Yes	15	PE7088-15	$336.52				
						Yes	20	PE7088-20	$308.78				
						Yes	30	PE7088-30	$331.55				
	BNC Male	BNC Female	2 GHz	Nickel Plated Brass	1.2:1	Yes	1	PE7000-1	$56.38				7
						Yes	2	PE7000-2	$57.46				
						Yes	3	PE7000-3	$59.92				
						Yes	6	PE7000-6	$58.36				
						Yes	10	PE7000-10	$56.79				
						Yes	20	PE7000-20	$55.73				
						Yes	30	PE7000-30	$58.36				

*** Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.**

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Attenuators

50 Ohm

Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
1 W	N Male	N Female	3 GHz	Nickel Plated Brass	1.2:1	Yes	1	PE7002-1	$103.53	See Web for Volume Pricing	8
						Yes	2	PE7002-2	$103.53		
						Yes	3	PE7002-3	$91.19		
						Yes	6	PE7002-6	$93.19		
						Yes	10	PE7002-10	$91.20		
						Yes	20	PE7002-20	$93.19		
						Yes	30	PE7002-30	$93.19		
						Yes	40	PE7002-40	$103.53		
	QMA Male	QMA Female	6 GHz	Tri-Metal Plated Brass			12	PE7AP1002-12	$96.65		9
							15	PE7AP1002-15	$100.42		
							0	PE7AP1002-0	$100.42		
							20	PE7AP1002-20	$100.42		
							1	PE7AP1002-1	$96.65		
							2	PE7AP1002-2	$96.65		
							3	PE7AP1002-3	$96.65		
							6	PE7AP1002-6	$100.42		
							9	PE7AP1002-9	$100.42		
	QN Male	QN Female	3 GHz				0	PE7AP1000-0	$133.67		10
							1	PE7AP1000-1	$133.67		
							2	PE7AP1000-2	$133.67		
							3	PE7AP1000-3	$133.67		
							6	PE7AP1000-6	$140.96		
							9	PE7AP1000-9	$140.96		
							12	PE7AP1000-12	$133.67		
							15	PE7AP1000-15	$133.67		
							18	PE7AP1000-18	$133.67		
							20	PE7AP1000-20	$140.96		
	SMA Male	SMA Female	2 GHz		1.2:1	Yes	1	PE7161-1	$73.97		11
						Yes	2	PE7161-2	$72.58		
						Yes	3	PE7161-3	$70.08		
						Yes	4	PE7161-4	$73.97		
						Yes	5	PE7161-5	$72.58		
						Yes	6	PE7161-6	$66.23		
						Yes	8	PE7161-8	$57.90		
						Yes	9	PE7161-9	$60.51		
						Yes	10	PE7161-10	$71.11		
						Yes	12	PE7161-12	$64.85		
						Yes	20	PE7161-20	$69.20		
				Passivated Stainless Steel		Yes	30	PE7161-30	$71.11		
						Yes	40	PE7161-40	$74.60		
	TNC Male	TNC Female		Nickel Plated Brass		Yes	1	PE7003-1	$90.57		12
						Yes	10	PE7003-10	$83.09		
						Yes	20	PE7003-20	$77.80		
						Yes	30	PE7003-30	$85.37		
						Yes	40	PE7003-40	$86.25		
2 W	2.92mm Male	2.92mm Female	26.5 GHz	Passivated Stainless Steel	1.4:1	Yes	1	PE7024-1	$331.65		13
						Yes	2	PE7024-2	$331.65		
						Yes	3	PE7024-3	$321.92		
						Yes	6	PE7024-6	$321.92		
						Yes	10	PE7024-10	$314.06		
						Yes	20	PE7024-20	$321.92		
						Yes	30	PE7024-30	$315.62		
				Stainless Steel		Yes	30	PE7024/SP-30	$216.75		14
			40 GHz	Passivated Stainless Steel		Yes	3	PE7090-3	$464.91		15
						Yes	10	PE7090-10	$433.91		
						Yes	15	PE7090-15	$464.91		
						Yes	20	PE7090-20	$433.91		
						Yes	30	PE7090-30	$419.40		
					1.6:1		0-0	PE7395-0	$200.00		16
							1-1	PE7395-1	$205.49		
							2-2	PE7395-2	$205.49		
							3-3	PE7395-3	$199.97		
							4-4	PE7395-4	$198.85		
							5-5	PE7395-5	$198.85		
							6-6	PE7395-6	$196.81		
							7-7	PE7395-7	$235.03		
							8-8	PE7395-8	$235.03		
							9-9	PE7395-9	$198.85		
							10-10	PE7395-10	$199.97		
							12-12	PE7395-12	$211.57		

*** Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.**

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Attenuators

50 Ohm

Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
2 W	2.92mm Male	2.92mm Female	40 GHz	Passivated Stainless Steel	1.6:1		15-15	PE7395-15	$202.28	See Web for Volume Pricing			16
							20-20	PE7395-20	$205.49				
	BNC Male	BNC Female	4 GHz	Nickel Plated Brass	1.25:1	Yes	1	PE7049-1	$126.44				17
						Yes	2	PE7049-2	$125.81				
						Yes	3	PE7049-3	$119.55				
						Yes	6	PE7049-6	$119.55				
						Yes	10	PE7049-10	$130.02				
						Yes	20	PE7049-20	$119.55				
						Yes	30	PE7049-30	$120.15				
	N Male	N Female	18 GHz	Passivated Stainless Steel	1.35:1	Yes	1	PE7004-1	$236.44				18
						Yes	2	PE7004-2	$235.44				
						Yes	3	PE7004-3	$220.09				
						Yes	4	PE7004-4	$235.44				
						Yes	5	PE7004-5	$236.44				
						Yes	6	PE7004-6	$216.63				
						Yes	7	PE7004-7	$232.94				
						Yes	8	PE7004-8	$190.55				
						Yes	9	PE7004-9	$207.70				
						Yes	10	PE7004-10	$202.65				
						Yes	12	PE7004-12	$222.99				
						Yes	15	PE7004-15	$228.46				
						Yes	20	PE7004-20	$220.09				
						Yes	30	PE7004-30	$219.87				
						Yes	40	PE7004-40	$235.44				
						Yes	2	PE7047-2	$185.62				19
						Yes	3	PE7047-3	$171.58				
						Yes	4	PE7047-4	$182.88				
						Yes	5	PE7047-5	$185.62				
						Yes	6	PE7047-6	$173.16				
						Yes	7	PE7047-7	$170.29				
						Yes	8	PE7047-8	$147.97				
						Yes	9	PE7047-9	$165.72				
						Yes	10	PE7047-10	$178.95				
						Yes	12	PE7047-12	$177.94				
						Yes	15	PE7047-15	$190.64				
						Yes	20	PE7047-20	$174.15				
						Yes	30	PE7047-30	$174.15				
						Yes	40	PE7047-40	$185.62				
	SMA Male	SMA Female	6 GHz	Copper	1.07:1		3	PE70A1009	$150.86				20
					1.15:1		3	PE70A1010	$60.24				21
					1.07:1		6	PE70A1011	$159.67				22
					1.15:1		6	PE70A1012	$60.24				23
				Brass	1.22:1		12	PE70A1014	$60.24				24
							16	PE70A1015	$65.60				25
			3 GHz	Passivated Stainless Steel	1.2:1	Yes	1	PE7001-1	$100.76				26
						Yes	2	PE7001-2	$100.76				
						Yes	3	PE7001-3	$89.93				
						Yes	4	PE7001-4	$98.93				
						Yes	5	PE7001-5	$103.53				
						Yes	6	PE7001-6	$94.95				
						Yes	7	PE7001-7	$103.53				
						Yes	8	PE7001-8	$84.77				
						Yes	9	PE7001-9	$94.95				
						Yes	10	PE7001-10	$93.41				
						Yes	12	PE7001-12	$94.95				
						Yes	15	PE7001-15	$94.95				
						Yes	20	PE7001-20	$93.41				
						Yes	30	PE7001-30	$94.95				
						Yes	40	PE7001-40	$103.53				
			6 GHz		1.35:1	Yes	0	PE7091-0	$42.24				27
						Yes	1	PE7091-1	$46.55				
						Yes	2	PE7091-2	$51.47				
						Yes	3	PE7091-3	$39.84				
						Yes	4	PE7091-4	$51.47				
						Yes	5	PE7091-5	$51.41				
						Yes	6	PE7091-6	$43.09				
						Yes	7	PE7091-7	$51.47				
						Yes	10	PE7091-10	$46.75				
						Yes	12	PE7091-12	$45.62				
						Yes	15	PE7091-15	$44.76				

*** Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.**

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Attenuators

50 Ohm

Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
2 W	SMA Male	SMA Female	6 GHz	Passivated Stainless Steel	1.35:1	Yes	20	PE7091-20	$45.02	See Web for Volume Pricing	27
						Yes	30	PE7091-30	$46.78		
						Yes	40	PE7091-40	$57.05		
						Yes	1	PE7162-1	$53.71		28
						Yes	2	PE7162-2	$53.60		
						Yes	3	PE7162-3	$29.56		
						Yes	4	PE7162-4	$52.64		
						Yes	5	PE7162-5	$53.29		
						Yes	6	PE7162-6	$33.67		
						Yes	7	PE7162-7	$49.72		
						Yes	8	PE7162-8	$49.72		
						Yes	9	PE7162-9	$45.52		
						Yes	10	PE7162-10	$39.97		
						Yes	12	PE7162-12	$47.36		
						Yes	15	PE7162-15	$48.26		
						Yes	20	PE7162-20	$39.80		
						Yes	30	PE7162-30	$47.44		
						Yes	40	PE7162-40	$54.74		
			12.4 GHz		1.25:1	Yes	1	PE7045-1	$137.46		29
						Yes	2	PE7045-2	$135.80		
						Yes	3	PE7045-3	$123.34		
						Yes	4	PE7045-4	$124.58		
						Yes	5	PE7045-5	$137.46		
						Yes	6	PE7045-6	$124.86		
						Yes	7	PE7045-7	$117.10		
						Yes	8	PE7045-8	$104.97		
						Yes	9	PE7045-9	$117.10		
						Yes	10	PE7045-10	$122.05		
						Yes	12	PE7045-12	$117.10		
						Yes	15	PE7045-15	$126.73		
						Yes	20	PE7045-20	$126.73		
						Yes	30	PE7045-30	$126.73		
						Yes	40	PE7045-40	$134.15		
			18 GHz		1.35:1	Yes	1	PE7005-1	$74.13		30
						Yes	2	PE7005-2	$69.20		
						Yes	3	PE7005-3	$67.46		
						Yes	4	PE7005-4	$81.15		
						Yes	5	PE7005-5	$75.52		
						Yes	6	PE7005-6	$71.39		
						Yes	7	PE7005-7	$82.03		
						Yes	8	PE7005-8	$82.03		
						Yes	9	PE7005-9	$72.73		
						Yes	10	PE7005-10	$67.46		
						Yes	12	PE7005-12	$76.37		
						Yes	15	PE7005-15	$67.35		
						Yes	20	PE7005-20	$66.97		
						Yes	30	PE7005-30	$69.30		
						Yes	40	PE7005-40	$79.79		
						Yes	1	PE7092-1	$51.41		31
						Yes	2	PE7092-2	$51.41		
						Yes	3	PE7092-3	$44.10		
						Yes	4	PE7092-4	$52.80		
						Yes	5	PE7092-5	$53.06		
						Yes	6	PE7092-6	$46.75		
						Yes	7	PE7092-7	$52.63		
						Yes	8	PE7092-8	$49.82		
						Yes	9	PE7092-9	$44.76		
						Yes	10	PE7092-10	$46.75		
						Yes	12	PE7092-12	$45.62		
						Yes	15	PE7092-15	$51.65		
						Yes	20	PE7092-20	$46.75		
						Yes	30	PE7092-30	$45.68		
						Yes	40	PE7092-40	$67.77		
			26 GHz		1.4:1	Yes	0	PE7087-0	$109.45		32
						Yes	1	PE7087-1	$123.16		
						Yes	2	PE7087-2	$123.16		
						Yes	3	PE7087-3	$104.36		
						Yes	4	PE7087-4	$122.07		
						Yes	5	PE7087-5	$120.26		
						Yes	6	PE7087-6	$107.86		

*** Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.**

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Attenuators

50 Ohm

Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
2 W	SMA Male	SMA Female	26 GHz	Passivated Stainless Steel	1.4:1	Yes	7	PE7087-7	$122.07	See Web for Volume Pricing	32
						Yes	8	PE7087-8	$122.07		
						Yes	9	PE7087-9	$115.22		
						Yes	10	PE7087-10	$106.27		
						Yes	12	PE7087-12	$116.59		
						Yes	15	PE7087-15	$123.16		
						Yes	20	PE7087-20	$107.86		
						Yes	30	PE7087-30	$107.86		
	TNC Male	TNC Female	2 GHz	Nickel Plated Brass	1.15:1	Yes	2	PE7003-2	$80.80		33
						Yes	3	PE7003-3	$76.22		
						Yes	6	PE7003-6	$85.37		
			12.4 GHz		1.25:1	Yes	1	PE7051-1	$185.62		34
						Yes	2	PE7051-2	$185.62		
						Yes	3	PE7051-3	$165.22		
						Yes	6	PE7051-6	$169.98		
						Yes	10	PE7051-10	$170.96		
						Yes	20	PE7051-20	$189.48		
						Yes	30	PE7051-30	$183.88		
						Yes	40	PE7051-40	$170.29		
			18 GHz	Passivated Stainless Steel	1.35:1	Yes	1	PE7030-1	$268.86		35
						Yes	2	PE7030-2	$307.42		
						Yes	3	PE7030-3	$319.42		
						Yes	6	PE7030-6	$319.42		
						Yes	10	PE7030-10	$319.42		
						Yes	20	PE7030-20	$322.63		
						Yes	30	PE7030-30	$293.06		
5 W	7/16 DIN Male	7/16 DIN Female	7.5 GHz	Tri-Metal Plated Brass	1.25:1	Yes	3	PE7039-3	$224.06		36
						Yes	6	PE7039-6	$224.06		
						Yes	10	PE7039-10	$244.23		
						Yes	20	PE7039-20	$224.06		
						Yes	30	PE7039-30	$291.03		
	N Male	N Female	3 GHz	Aluminum	1.2:1	Yes	1	PE7390-1	$74.15		37
						Yes	2	PE7390-2	$74.15		
						Yes	3	PE7390-3	$69.28		
						Yes	6	PE7390-6	$69.28		
						Yes	10	PE7390-10	$69.48		
						Yes	15	PE7390-15	$68.36		
						Yes	20	PE7390-20	$69.28		
						Yes	30	PE7390-30	$67.98		
			6 GHz	Black Anodized Aluminum Heatsink	1.25:1		1	PE7AP006-01	$114.40		38
							2	PE7AP006-02	$118.87		
							3	PE7AP006-03	$113.15		
							4	PE7AP006-04	$118.87		
							5	PE7AP006-05	$118.87		
							6	PE7AP006-06	$113.15		
							9	PE7AP006-09	$109.78		
							10	PE7AP006-10	$114.06		
							12	PE7AP006-12	$109.78		
							15	PE7AP006-15	$103.40		
							20	PE7AP006-20	$144.56		
							30	PE7AP006-30	$114.06		
							40	PE7AP006-40	$125.48		
			18 GHz		1.4:1	Yes	1	PE7014-1	$318.86		39
						Yes	2	PE7014-2	$318.86		
						Yes	3	PE7014-3	$335.10		
						Yes	6	PE7014-6	$335.10		
						Yes	10	PE7014-10	$328.96		
						Yes	20	PE7014-20	$335.10		
						Yes	30	PE7014-30	$328.96		
						Yes	40	PE7014-40	$347.55		
	SMA Male	SMA Female	3 GHz		1.2:1	Yes	1	PE7391-1	$71.84		40
						Yes	2	PE7391-2	$74.15		
						Yes	3	PE7391-3	$68.36		
				Aluminum		Yes	6	PE7391-6	$68.36		
						Yes	10	PE7391-10	$68.36		
				Black Anodized Aluminum Heatsink		Yes	15	PE7391-15	$68.36		
				Aluminum		Yes	20	PE7391-20	$69.28		
						Yes	30	PE7391-30	$67.98		

*** Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.**

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Attenuators

50 Ohm

Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
5 W	SMA Male	SMA Female	18 GHz	Black Anodized Aluminum Heatsink	1.35:1	Yes	1	PE7013-1	$188.98	See Web for Volume Pricing	41
						Yes	2	PE7013-2	$198.07		
						Yes	3	PE7013-3	$178.05		
						Yes	6	PE7013-6	$182.82		
						Yes	10	PE7013-10	$178.26		
						Yes	20	PE7013-20	$183.18		
						Yes	30	PE7013-30	$178.05		
						Yes	40	PE7013-40	$199.07		
	TNC Male	TNC Female				Yes	1	PE7052-1	$317.64		42
						Yes	2	PE7052-2	$330.35		
						Yes	3	PE7052-3	$330.35		
						Yes	6	PE7052-6	$330.35		
						Yes	10	PE7052-10	$330.35		
						Yes	20	PE7052-20	$330.35		
						Yes	30	PE7052-30	$330.28		
10 W	2.92mm Male	2.92mm Female	40 GHz	Black Anodized Aluminum Heatsink	1.5:1	No	10	PE7AP402-10	$1,039.72		43
						No	20	PE7AP402-20	$984.98		
						Yes	3	PE7AP402-3	$1,022.76		
						Yes	6	PE7AP402-6	$1,022.73		
						No	30	PE7AP402-30	$1,039.72		
	7/16 DIN Male	7/16 DIN Female	7.5 GHz		1.45:1	Yes	6	PE7040-6	$318.76		44
						Yes	10	PE7040-10	$368.21		
						Yes	20	PE7040-20	$209.29		
	BNC Male	BNC Female	2 GHz		1.6:1	Yes	2	PE7025-2	$341.71		45
						Yes	3	PE7025-3	$360.01		
						Yes	6	PE7025-6	$343.50		
						Yes	10	PE7025-10	$353.41		
						Yes	20	PE7025-20	$348.19		
						Yes	30	PE7025-30	$336.87		
						Yes	40	PE7025-40	$395.19		
	N Male	N Female				Yes	2	PE7010-2	$250.28		46
						Yes	3	PE7010-3	$261.35		
						Yes	6	PE7010-6	$261.35		
						Yes	10	PE7010-10	$261.35		
						Yes	20	PE7010-20	$261.35		
						Yes	30	PE7010-30	$260.37		
						Yes	40	PE7010-40	$217.67		
			3 GHz		1.2:1	Yes	3	PE7386-3	$156.51		47
						Yes	6	PE7386-6	$158.86		
						Yes	10	PE7386-10	$158.86		
						Yes	15	PE7386-15	$130.63		
						Yes	20	PE7386-20	$158.86		
						Yes	30	PE7386-30	$158.86		
						Yes	40	PE7386-40	$170.29		
			12.4 GHz		1.35:1	Yes	1	PE7048-1	$414.54		48
						Yes	2	PE7048-2	$414.54		
						Yes	3	PE7048-3	$409.84		
						Yes	6	PE7048-6	$408.25		
						Yes	10	PE7048-10	$402.32		
						Yes	20	PE7048-20	$402.92		
						Yes	30	PE7048-30	$391.98		
						Yes	40	PE7048-40	$402.92		
			18 GHz		1.4:1	Yes	1	PE7015-1	$314.13		49
						Yes	2	PE7015-2	$328.49		
						Yes	3	PE7015-3	$402.92		
						Yes	6	PE7015-6	$403.87		
						Yes	10	PE7015-10	$396.97		
						Yes	20	PE7015-20	$390.26		
						Yes	30	PE7015-30	$403.87		
						Yes	40	PE7015-40	$414.81		
	SMA Male	SMA Female	6 GHz		1.2:1		1	PE7428-01	$185.89		50
							2	PE7428-02	$170.49		
							3	PE7428-03	$166.12		
							6	PE7428-06	$219.12		
							10	PE7428-10	$172.60		
							15	PE7428-15	$172.60		
							20	PE7428-20	$172.60		
							30	PE7428-30	$172.60		
			18 GHz		1.4:1	Yes	1	PE7016-1	$402.32		51
						Yes	2	PE7016-2	$367.67		

*** Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.**

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Attenuators

50 Ohm

Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
10 W	SMA Male	SMA Female	18 GHz	Black Anodized Aluminum Heatsink	1.4:1	Yes	3	PE7016-3	$380.10	See Web for Volume Pricing	51
						Yes	6	PE7016-6	$372.79		
						Yes	10	PE7016-10	$371.17		
						Yes	20	PE7016-20	$372.98		
						Yes	30	PE7016-30	$380.10		
						Yes	40	PE7016-40	$402.92		
	TNC Male	TNC Female				Yes	6	PE7053-6	$461.14		52
						Yes	10	PE7053-10	$472.16		
						Yes	20	PE7053-20	$513.28		
						Yes	40	PE7053-40	$505.56		
15 W	4.3-10 Male	4.3-10 Female	6 GHz	Aluminum	1.15:1		10	PE7AP1001-10	$342.85		53
							3	PE7AP1001-3	$312.38		
							6	PE7AP1001-6	$312.38		
							20	PE7AP1001-20	$312.38		
25 W	7/16 DIN Male	7/16 DIN Female	6 GHz	Black Anodized Aluminum Heatsink	1.3:1	Yes	50	PE7379-50	$473.89		54
			7.5 GHz		1.45:1	Yes	10	PE7041-10	$618.25		55
						Yes	10	PE7379-10	$619.79		56
						Yes	20	PE7379-20	$497.10		
						Yes	30	PE7379-30	$473.89		
						Yes	40	PE7379-40	$473.89		
						Yes	3	PE7379-3	$480.99		
						Yes	6	PE7379-6	$473.89		
	7/16 DIN Female		6 GHz		1.3:1	Yes	50	PE7380-50	$480.74		57
			7.5 GHz		1.45:1	Yes	3	PE7380-3	$480.74		
						Yes	6	PE7380-6	$480.74		
						Yes	10	PE7380-10	$480.74		
						Yes	20	PE7380-20	$480.74		
						Yes	30	PE7380-30	$480.74		
						Yes	40	PE7380-40	$480.74		
	N Male		6 GHz		1.3:1	Yes	50	PE7366-50	$419.53		58
			7.5 GHz		1.45:1	Yes	10	PE7366-10	$419.53		
						Yes	20	PE7366-20	$419.53		
						Yes	30	PE7366-30	$442.42		
						Yes	40	PE7366-40	$442.42		
						Yes	3	PE7366-3	$419.53		
						Yes	6	PE7366-6	$419.53		
		N Female	4 GHz		1.25:1	Yes	1	PE7392-1	$227.43		59
						Yes	2	PE7392-2	$227.43		
						Yes	3	PE7392-3	$213.25		
						Yes	6	PE7392-6	$216.00		
						Yes	10	PE7392-10	$216.00		
						Yes	20	PE7392-20	$216.91		
						Yes	30	PE7392-30	$216.91		
						Yes	40	PE7392-40	$227.43		
			8 GHz		1.6:1	Yes	50	PE7367-50	$490.27		60
			18 GHz		1.4:1	Yes	1	PE7017-1	$581.34		61
						Yes	2	PE7017-2	$670.51		
						Yes	3	PE7017-3	$590.05		
						Yes	6	PE7017-6	$585.68		
						Yes	10	PE7017-10	$590.05		
						Yes	20	PE7017-20	$581.34		
						Yes	30	PE7017-30	$590.05		
						Yes	40	PE7017-40	$684.32		
					1.35:1	Yes	3	PE7426-03	$340.76		62
						Yes	6	PE7426-06	$346.26		
					1.45:1	Yes	10	PE7367-10	$485.57		63
					1.35:1	Yes	10	PE7426-10	$354.45		64
					1.6:1	Yes	20	PE7367-20	$485.57		65
					1.35:1	Yes	20	PE7426-20	$360.08		66
					1.6:1	Yes	30	PE7367-30	$473.72		67
					1.35:1	Yes	30	PE7426-30	$346.23		68
					1.6:1	Yes	40	PE7367-40	$490.27		69
					1.35:1	Yes	40	PE7426-40	$371.34		70
					1.6:1	Yes	3	PE7367-3	$485.57		71
						Yes	6	PE7367-6	$485.57		
	N Female	7/16 DIN Male	6 GHz		1.3:1	Yes	50	PE7370-50	$411.23		72
			7.5 GHz		1.45:1	Yes	3	PE7370-3	$411.23		
						Yes	6	PE7370-6	$411.23		
						Yes	10	PE7370-10	$411.23		
						Yes	20	PE7370-20	$411.23		

*** Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.**

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Attenuators

50 Ohm

Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
25 W	N Female	7/16 DIN Male	7.5 GHz	Black Anodized Aluminum Heatsink	1.45:1	Yes	30	PE7370-30	$411.23	See Web for Volume Pricing	72
						Yes	40	PE7370-40	$411.23		
		7/16 DIN Female	6 GHz		1.3:1	Yes	50	PE7369-50	$418.08		73
			7.5 GHz		1.45:1	Yes	10	PE7369-10	$418.08		
						Yes	20	PE7369-20	$418.08		
						Yes	30	PE7369-30	$418.08		
						Yes	40	PE7369-40	$418.08		
						Yes	3	PE7369-3	$418.08		
						Yes	6	PE7369-6	$418.08		
		N Female	8 GHz		1.6:1	Yes	50	PE7371-50	$393.24		74
			18 GHz		1.45:1	Yes	10	PE7371-10	$461.11		
					1.6:1	Yes	3	PE7371-3	$461.11		
						Yes	6	PE7371-6	$461.11		
						Yes	20	PE7371-20	$460.57		
						Yes	30	PE7371-30	$460.57		
						Yes	40	PE7371-40	$478.85		
		TNC Female				Yes	30	PE7372-30	$401.46		75
	SMA Male	SMA Female	4 GHz		1.25:1	Yes	3	PE7393-3	$167.92		76
						Yes	10	PE7393-10	$206.54		
						Yes	20	PE7393-20	$206.54		
						Yes	30	PE7393-30	$206.54		
						Yes	40	PE7393-40	$224.07		
			6 GHz		1.3:1	Yes	50	PE7357-50	$362.55		77
			18 GHz		1.4:1	Yes	1	PE7018-1	$570.27		78
						Yes	2	PE7018-2	$570.27		
						Yes	3	PE7018-3	$650.58		
						Yes	6	PE7018-6	$640.98		
						Yes	10	PE7018-10	$650.58		
						Yes	20	PE7018-20	$572.50		
						Yes	30	PE7018-30	$650.58		
						Yes	40	PE7018-40	$684.32		
					1.6:1	Yes	10	PE7357-10	$445.94		79
						Yes	20	PE7357-20	$362.55		
						Yes	30	PE7357-30	$445.94		
						Yes	40	PE7357-40	$455.98		
						Yes	3	PE7357-3	$445.94		
						Yes	6	PE7357-6	$345.63		
	SMA Female					Yes	10	PE7363-10	$442.09		80
						Yes	20	PE7363-20	$442.09		
						Yes	30	PE7363-30	$442.09		
						Yes	6	PE7363-6	$435.57		
						Yes	40	PE7363-40	$478.85		
	TNC Male	TNC Female			1.4:1	Yes	10	PE7054-10	$818.90		81
						Yes	20	PE7054-20	$775.78		
						Yes	30	PE7054-30	$775.78		
					1.6:1	Yes	20	PE7375-20	$426.54		82
						Yes	30	PE7375-30	$406.62		
						Yes	40	PE7375-40	$421.69		
50 W	7/16 DIN Male	7/16 DIN Female	6 GHz	Black Anodized Aluminum Heatsink	1.3:1	No	50	PE7312-50	$523.42		83
			7.5 GHz		1.45:1	No	10	PE7042-10	$717.13		84
						No	30	PE7042-30	$661.69		
						No	3	PE7312-3	$549.08		85
						No	6	PE7312-6	$523.42		
						No	10	PE7312-10	$549.08		
						No	20	PE7312-20	$551.97		
						No	30	PE7312-30	$523.42		
						No	40	PE7312-40	$523.42		
	7/16 DIN Female	7/16 DIN Male	6 GHz		1.3:1	No	50	PE7310-50	$523.42		86
			7.5 GHz		1.45:1	No	3	PE7310-3	$549.08		
						No	6	PE7310-6	$523.42		
						No	10	PE7310-10	$549.08		
						No	20	PE7310-20	$523.42		
						No	30	PE7310-30	$523.42		
						No	40	PE7310-40	$523.42		
		7/16 DIN Female	6 GHz		1.3:1	No	50	PE7313-50	$530.30		87
			7.5 GHz		1.45:1	No	3	PE7313-3	$530.30		
						No	6	PE7313-6	$626.34		
						No	10	PE7313-10	$530.30		

*** Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.**

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Attenuators

50 Ohm

Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
50 W	7/16 DIN Female	7/16 DIN Female	7.5 GHz	Black Anodized Aluminum Heatsink	1.45:1	No	20	PE7313-20	$530.30	See Web for Volume Pricing	87
						No	30	PE7313-30	$530.30		
						No	40	PE7313-40	$626.34		
		N Female	6 GHz		1.3:1	No	50	PE7316-50	$492.04		88
						No	50	PE7321-50	$467.67		89
			7.5 GHz		1.45:1	No	3	PE7316-3	$469.06		90
						No	6	PE7316-6	$469.06		
						No	10	PE7316-10	$469.06		
						No	20	PE7316-20	$469.06		
						No	30	PE7316-30	$469.06		
						No	40	PE7316-40	$469.06		
			18 GHz		1.6:1	No	3	PE7321-3	$467.67		91
						No	6	PE7321-6	$467.67		
						No	10	PE7321-10	$467.67		
						No	20	PE7321-20	$467.67		
						No	30	PE7321-30	$467.67		
						No	40	PE7321-40	$467.67		
	N Male	7/16 DIN Female	6 GHz		1.3:1	No	50	PE7314-50	$469.06		92
			7.5 GHz		1.45:1	No	3	PE7314-3	$469.06		
						No	6	PE7314-6	$469.06		
						No	10	PE7314-10	$469.06		
						No	20	PE7314-20	$469.06		
						No	30	PE7314-30	$476.09		
						No	40	PE7314-40	$469.06		
		N Female	3 GHz		1.15:1	No	3	PE7388-3	$272.71		93
						No	6	PE7388-6	$272.71		
						No	10	PE7388-10	$279.74		
						No	15	PE7388-15	$279.74		
						No	20	PE7388-20	$280.87		
						No	30	PE7388-30	$270.22		
						No	40	PE7388-40	$300.34		
						Yes	3	PE7389-3	$238.85		94
						Yes	6	PE7389-6	$238.85		
						Yes	10	PE7389-10	$238.85		
						Yes	15	PE7389-15	$238.85		
						Yes	20	PE7389-20	$236.23		
						Yes	30	PE7389-30	$239.78		
						Yes	40	PE7389-40	$251.20		
			4 GHz		1.35:1	Yes	2	PE7394-2	$314.28		95
						Yes	3	PE7394-3	$366.05		
						Yes	6	PE7394-6	$297.60		
						Yes	10	PE7394-10	$297.60		
						Yes	30	PE7394-30	$312.78		
						Yes	40	PE7394-40	$315.12		
			6 GHz		1.3:1	No	50	PE7322-50	$499.54		96
			18 GHz		1.45:1	No	6	PE7019-6	$644.79		97
						No	10	PE7019-10	$707.90		
						No	20	PE7019-20	$687.01		
						No	30	PE7019-30	$664.40		
						No	40	PE7019-40	$651.93		
					1.6:1	No	3	PE7322-3	$570.27		98
						No	6	PE7322-6	$570.27		
						No	10	PE7322-10	$570.27		
						No	20	PE7322-20	$662.20		
						No	30	PE7322-30	$573.10		
						No	40	PE7322-40	$499.54		
	N Female	7/16 DIN Male	6 GHz		1.3:1	No	50	PE7311-50	$485.94		99
			7.5 GHz		1.45:1	No	3	PE7311-3	$460.80		
						No	6	PE7311-6	$460.80		
						No	10	PE7311-10	$460.80		
						No	20	PE7311-20	$478.77		
						No	30	PE7311-30	$478.77		
						No	40	PE7311-40	$460.80		
		7/16 DIN Female	6 GHz		1.3:1	No	50	PE7315-50	$467.67		1
			7.5 GHz		1.45:1	No	3	PE7315-3	$467.67		
						No	6	PE7315-6	$467.67		
						No	10	PE7315-10	$467.67		
						No	20	PE7315-20	$467.67		
						No	30	PE7315-30	$467.67		
						No	40	PE7315-40	$490.60		

*** Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.**

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Attenuators

50 Ohm

Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
50 W	N Female	N Male	6 GHz	Black Anodized Aluminum Heatsink	1.3:1	No	50	PE7317-50	$588.55	See Web for Volume Pricing	2
			18 GHz		1.6:1	No	3	PE7317-3	$561.85		
						No	6	PE7317-6	$570.27		
						No	10	PE7317-10	$570.27		
						No	20	PE7317-20	$591.01		
						No	30	PE7317-30	$570.27		
						No	40	PE7317-40	$581.69		
		N Female	6 GHz		1.3:1	No	50	PE7323-50	$474.61		3
			18 GHz		1.6:1	No	3	PE7323-3	$497.85		
						No	6	PE7323-6	$497.85		
						No	10	PE7323-10	$576.26		
						No	20	PE7323-20	$661.30		
						No	30	PE7323-30	$578.98		
						No	40	PE7323-40	$581.69		
	SMA Male	SMA Female			1.45:1	No	6	PE7020-6	$766.61		4
						No	10	PE7020-10	$766.61		
						No	20	PE7020-20	$684.18		
						No	30	PE7020-30	$676.95		
						No	40	PE7020-40	$674.93		
					1.35:1	Yes	3	PE7427-03	$580.18		5
						Yes	6	PE7427-06	$571.62		
						Yes	10	PE7427-10	$580.18		
						Yes	15	PE7427-15	$550.16		
						Yes	20	PE7427-20	$580.18		
						Yes	30	PE7427-30	$580.18		
						Yes	40	PE7427-40	$558.40		
	SMA Female				1.6:1	No	6	PE7337-6	$552.33		6
						No	10	PE7337-10	$552.33		
						No	20	PE7337-20	$552.33		
						No	30	PE7337-30	$552.33		
						No	40	PE7337-40	$558.84		
						No	50	PE7337-50	$656.95		
	TNC Male	TNC Female			1.45:1	No	30	PE7055-30	$833.12		7
						No	40	PE7055-40	$807.94		
	TNC Female				1.6:1	No	10	PE7351-10	$529.45		8
						No	20	PE7351-20	$529.45		
						No	40	PE7351-40	$635.33		
						No	50	PE7351-50	$529.45		
100 W	7/16 DIN Male	7/16 DIN Female	6 GHz	Black Anodized Aluminum Heatsink	1.45:1	No	3	PE7203-3	$886.12		9
						No	6	PE7203-6	$840.27		
						No	10	PE7203-10	$886.12		
						No	20	PE7203-20	$929.55		
						No	30	PE7203-30	$840.27		
						No	40	PE7203-40	$946.94		
						No	50	PE7203-50	$946.94		
						No	60	PE7203-60	$1,026.87		
		N Female				No	3	PE7211-3	$768.73		10
						No	6	PE7211-6	$768.73		
						No	10	PE7211-10	$768.73		
						No	20	PE7211-20	$768.73		
						No	30	PE7211-30	$806.41		
						No	40	PE7211-40	$1,017.34		
						No	50	PE7211-50	$1,017.34		
						No	60	PE7211-60	$826.35		
	7/16 DIN Female	7/16 DIN Male				No	3	PE7201-3	$852.86		11
						No	6	PE7201-6	$852.86		
						No	10	PE7201-10	$886.12		
						No	20	PE7201-20	$881.46		
						No	30	PE7201-30	$840.27		
						No	40	PE7201-40	$897.95		
						No	50	PE7201-50	$897.95		
						No	60	PE7201-60	$911.40		
		7/16 DIN Female				No	3	PE7204-3	$848.15		12
						No	6	PE7204-6	$848.15		
						No	10	PE7204-10	$848.15		
						No	20	PE7204-20	$848.15		
						No	30	PE7204-30	$848.15		
						No	40	PE7204-40	$905.81		
						No	50	PE7204-50	$905.81		
						No	60	PE7204-60	$905.81		

*** Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.**

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Attenuators

50 Ohm

Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
100 W	7/16 DIN Female	N Male	6 GHz	Black Anodized Aluminum Heatsink	1.45:1	No	3	PE7207-3	$778.15	See Web for Volume Pricing			13
						No	6	PE7207-6	$778.15				
						No	10	PE7207-10	$778.15				
						No	20	PE7207-20	$778.15				
						No	30	PE7207-30	$778.15				
						No	40	PE7207-40	$835.83				
						No	50	PE7207-50	$835.83				
						No	60	PE7207-60	$835.83				
		N Female				No	3	PE7212-3	$776.59				14
						No	6	PE7212-6	$776.59				
						No	10	PE7212-10	$776.59				
						No	20	PE7212-20	$776.59				
						No	30	PE7212-30	$776.59				
						No	40	PE7212-40	$834.22				
						No	50	PE7212-50	$834.22				
						No	60	PE7212-60	$834.22				
	BNC Male	BNC Female	1,000 MHz		1.4:1	No	3	PE7026-3	$920.31				15
						No	6	PE7026-6	$930.04				
						No	10	PE7026-10	$821.70				
						No	20	PE7026-20	$930.04				
						No	30	PE7026-30	$855.97				
						No	40	PE7026-40	$930.04				
	N Male	7/16 DIN Female	6 GHz		1.45:1	No	3	PE7205-3	$778.15				16
						No	6	PE7205-6	$778.15				
						No	10	PE7205-10	$778.15				
						No	20	PE7205-20	$778.15				
						No	30	PE7205-30	$778.15				
						No	40	PE7205-40	$835.83				
						No	50	PE7205-50	$835.83				
						No	60	PE7205-60	$835.83				
		N Female	1.5 GHz		1.25:1	No	6	PE7021-6	$917.64				17
						No	10	PE7021-10	$795.13				
						No	20	PE7021-20	$779.84				
						No	30	PE7021-30	$843.41				
						No	40	PE7021-40	$825.78				
			3 GHz		1.3:1	Yes	3	PE7385-3	$478.85				18
						Yes	6	PE7385-6	$478.85				
						Yes	10	PE7385-10	$478.85				
						Yes	20	PE7385-20	$478.85				
						Yes	30	PE7385-30	$478.85				
						Yes	40	PE7385-40	$490.27				
			4 GHz		1.2:1	Yes	3	PE7421-3	$558.84				19
						Yes	6	PE7421-6	$558.84				
						Yes	10	PE7421-10	$570.27				
						Yes	20	PE7421-20	$562.75				
						Yes	30	PE7421-30	$604.56				
						No	40	PE7421-40	$699.17				
			6 GHz		1.45:1	No	3	PE7213-3	$745.16				20
						No	6	PE7213-6	$810.93				
						No	10	PE7213-10	$837.14				
						No	20	PE7213-20	$842.06				
						No	30	PE7213-30	$828.22				
						No	40	PE7213-40	$853.53				
						No	50	PE7213-50	$869.92				
						No	60	PE7213-60	$845.39				
			18 GHz			No	3	PE7424-03	$1,098.82				21
						No	6	PE7424-06	$955.83				
					1.35:1	No	10	PE7424-10	$934.85				
						No	20	PE7424-20	$967.70				
						No	30	PE7424-30	$1,005.44				
						No	40	PE7424-40	$1,017.07				
		TNC Female	6 GHz		1.45:1	No	30	PE7237-30	$749.42				22
	N Female	7/16 DIN Male				No	3	PE7202-3	$768.73				23
						No	6	PE7202-6	$768.73				
						No	10	PE7202-10	$768.73				
						No	20	PE7202-20	$768.73				
						No	30	PE7202-30	$810.67				
						No	40	PE7202-40	$826.35				
						No	50	PE7202-50	$826.35				

*** Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.**

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Attenuators

50 Ohm

Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
100 W	N Female	7/16 DIN Male	6 GHz	Black Anodized Aluminum Heatsink	1.45:1	No	60	PE7202-60	$826.35	See Web for Volume Pricing			23
		7/16 DIN Female				No	3	PE7206-3	$917.24				24
						No	6	PE7206-6	$776.59				
						No	10	PE7206-10	$776.59				
						No	20	PE7206-20	$917.25				
						No	30	PE7206-30	$776.59				
						No	40	PE7206-40	$834.22				
						No	50	PE7206-50	$834.22				
						No	60	PE7206-60	$834.22				
		N Male				No	3	PE7208-3	$781.68				25
						No	6	PE7208-6	$834.59				
						No	10	PE7208-10	$781.68				
						No	20	PE7208-20	$837.14				
						No	30	PE7208-30	$803.76				
						No	40	PE7208-40	$853.53				
						No	50	PE7208-50	$845.39				
						No	60	PE7208-60	$845.39				
		N Female				No	3	PE7214-3	$827.96				26
						No	6	PE7214-6	$811.26				
						No	10	PE7214-10	$819.83				
						No	20	PE7214-20	$827.96				
						No	30	PE7214-30	$827.96				
						No	40	PE7214-40	$843.68				
						No	50	PE7214-50	$875.48				
						No	60	PE7214-60	$856.01				
	SMA Male	SMA Female	1.5 GHz		1.25:1	No	6	PE7022-6	$920.31				27
						No	20	PE7022-20	$623.40				
						No	30	PE7022-30	$921.27				
						No	40	PE7022-40	$851.61				
			6 GHz		1.45:1	No	3	PE7227-3	$683.43				28
						No	6	PE7227-6	$673.34				
						No	10	PE7227-10	$673.34				
						No	20	PE7227-20	$673.34				
						No	30	PE7227-30	$673.34				
						No	40	PE7227-40	$730.94				
						No	50	PE7227-50	$770.82				
						No	60	PE7227-60	$836.83				
			18 GHz		1.35:1	No	10	PE7425-10	$1,061.67				29
						No	20	PE7425-20	$979.27				
						No	30	PE7425-30	$1,074.01				
						No	40	PE7425-40	$1,085.44				
	SMA Female	SMA Male	6 GHz		1.45:1	No	3	PE7221-3	$706.33				30
						No	6	PE7221-6	$733.88				
						No	10	PE7221-10	$744.87				
						No	20	PE7221-20	$744.87				
						No	40	PE7221-40	$808.58				
						No	50	PE7221-50	$766.76				
						No	60	PE7221-60	$836.83				
		SMA Female				No	3	PE7228-3	$741.29				31
						No	20	PE7228-20	$791.43				
						No	30	PE7228-30	$830.24				
						No	50	PE7228-50	$836.83				
	TNC Male	TNC Female	1.5 GHz		1.15:1	No	30	PE7056-30	$896.32				32
	TNC Female	N Male	6 GHz		1.45:1	No	30	PE7210-30	$721.29				33
		N Female				No	3	PE7218-3	$730.48				34
150 W	N Male	N Female	8 GHz	Black Anodized Aluminum Heatsink	1.5:1	No	3	PE7AP150-03	$725.73				35
						No	6	PE7AP150-06	$714.15				
						No	10	PE7AP150-10	$753.11				
						No	20	PE7AP150-20	$753.11				
						No	30	PE7AP150-30	$798.81				
						No	40	PE7AP150-40	$753.27				
200 W	N Male	N Female	3 GHz	Black Anodized Aluminum Heatsink	1.35:1	No	10	PE7387-10	$682.20				36
						No	20	PE7387-20	$684.54				
						No	30	PE7387-30	$685.46				
						No	40	PE7387-40	$708.16				

*** Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.**

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Attenuators

50 Ohm

Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1	2-4	5-9	10+	ROW
200 W	N Male	N Female	18 GHz	Black Anodized Aluminum Heatsink	1.5:1	No	20	PE7AP200-20	$2,943.63	$2,825.88	$2,708.14	$2,590.39	37
250 W	N Male	N Female	8.5 GHz	Black Anodized Aluminum Heatsink	1.45:1	No	10	PE7AP250-10	$912.68	$876.17	$839.67	$803.16	38
						No	20	PE7AP250-20	$948.26	$910.33	$872.40	$834.47	
						No	30	PE7AP250-30	$948.26	$910.33	$872.40	$834.47	
						No	40	PE7AP250-40	$1,027.50	$986.40	$945.30	$904.20	
300 W	N Male	N Female	1,000 MHz	Black Anodized Aluminum Heatsink	1.4:1	No	3	PE7031-3	$2,151.81	$2,065.74	$1,979.67	$1,893.59	39
						No	10	PE7031-10	$1,934.76	$1,857.37	$1,779.98	$1,702.59	
						No	30	PE7031-30	$2,012.14	$1,931.65	$1,851.17	$1,770.68	
500 W	N Male	N Female	1,000 MHz	Black Anodized Aluminum Heatsink	1.15:1	No	6	PE7032-6	$2,319.45	$2,238.27	$2,157.09	$2,087.51	40
						No	30	PE7032-30	$2,319.45	$2,238.27	$2,157.09	$2,087.51	
			2.4 GHz		1.35:1	No	2	PE7085-2	$2,513.02	$2,425.06	$2,337.11	$2,261.72	41
						No	20	PE7085-20	$2,056.14	$1,973.89	$1,891.65	$1,809.40	
			3 GHz		1.4:1	No	3	PE7AP418-03	$2,090.44	$2,017.27	$1,944.11	$1,881.40	42
					1.35:1	No	10	PE7AP418-10	$2,090.44	$2,006.82	$1,923.20	$1,839.59	
						No	20	PE7AP418-20	$2,090.44	$2,006.82	$1,923.20	$1,839.59	
						No	30	PE7AP418-30	$2,090.44	$2,006.82	$1,923.20	$1,839.59	
						No	40	PE7AP418-40	$2,090.44	$2,017.27	$1,944.11	$1,881.40	
1000 W	N Male	N Female	2.5 GHz	Black Aluminum Heatsink	1.35:1	No	30-30	PE7423-30	$4,020.22	$3,879.51	$3,738.80	$3,618.20	43
						No	40	PE7423-40	$4,020.22	$3,879.51	$3,738.80	$3,618.20	

75 Ohm

Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
1 W	BNC Male	BNC Female	1,000 MHz	Nickel Plated Brass	1.2:1	Yes	1	PE7009-1	$70.08	See Web for Volume Pricing	44
						Yes	2	PE7009-2	$70.08		
						Yes	3	PE7009-3	$62.40		
						Yes	6	PE7009-6	$64.62		
						Yes	10	PE7009-10	$63.58		
						Yes	20	PE7009-20	$63.58		
						Yes	30	PE7009-30	$63.58		
	N Male	N Female				Yes	3	PE7029-3	$84.77		45
						Yes	6	PE7029-6	$84.77		
						Yes	10	PE7029-10	$94.95		
						Yes	20	PE7029-20	$75.70		
						Yes	30	PE7029-30	$85.26		
2 W	BNC Male	BNC Female	4 GHz	Nickel Plated Brass	1.35:1	Yes	2	PE7050-2	$147.44		46
						Yes	3	PE7050-3	$136.01		
						Yes	6	PE7050-6	$136.01		
						Yes	10	PE7050-10	$163.20		
						Yes	20	PE7050-20	$163.20		
						Yes	30	PE7050-30	$136.01		
	F Male	F Female	1,000 MHz		1.3:1	Yes	1	PE7057-1	$92.87		47
						Yes	2	PE7057-2	$92.87		
						Yes	3	PE7057-3	$122.46		
						Yes	6	PE7057-6	$122.46		
						Yes	10	PE7057-10	$124.58		
			3 GHz	Tri-Metal Plated Brass			1	PE7396-1	$78.44		48
							2	PE7396-2	$79.93		
							3	PE7396-3	$75.07		
							4	PE7396-4	$95.92		
							5	PE7396-5	$91.35		
							6	PE7396-6	$74.15		
							7	PE7396-7	$95.92		
							8	PE7396-8	$95.92		
							9	PE7396-9	$88.97		
							10	PE7396-10	$89.90		
							16	PE7396-16	$95.92		
							20	PE7396-20	$74.15		
	N Male	N Female	4 GHz	Passivated Stainless Steel		Yes	1	PE7044-1	$170.29		49
						Yes	2	PE7044-2	$170.29		
						Yes	3	PE7044-3	$167.76		

*** Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.**

See Our Website For Current Pricing & Real-Time Stock Availability!

Fixed Attenuators

75 Ohm

Max. Power (Watts)	Connector Input	Connector Output	Max. Freq.	Construction Material	VSWR Max.	Bi-Dir.*	ATTN. (dB)	Model No	1-9	10--24	25-49	50+	ROW
2 W	N Male	N Female	4 GHz	Passivated Stainless Steel	1.3:1	Yes	6	PE7044-6	$190.64	$183.01	$177.30	$173.48	49
						Yes	10	PE7044-10	$167.76	$159.37	$150.98	$144.27	
						Yes	20	PE7044-20	$167.76	$159.37	$150.98	$144.27	
						Yes	30	PE7044-30	$167.76	$159.37	$150.98	$144.27	

Step Attenuators, Push Button

50 Ohm

Max. Power (Watts)	Conn. Input	Conn. Output	Frequency Range (MHz)	Construction Material	VSWR Max. (MHz)	ATTN. Range (dB)	Step Size (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
1 W	BNC Female	BNC Female	DC-750	Brass	DC-100: 1.1:1 100-300: 1.25:1 300-500: 1.25:1 500-750: 1.4:1	0-65	1.0	PE7008-1	$954.15		See Web for Volume Pricing		50
					1.4:1	0-82.5		PE70A1021	$1,521.12				51
					DC-100: 1.1:1 100-300: 1.25:1 300-500: 1.25:1 500-750: 1.4:1	0-45.5	0.5	PE7008-2	$1,001.74				52
					1.4:1	0-82.5	0.5	PE7008-6	$1,212.36				
						0-102	1.0	PE7008-5	$1,315.77				

75 Ohm

Max. Power (Watts)	Conn. Input	Conn. Output	Frequency Range (MHz)	Construction Material	VSWR Max. (MHz)	ATTN. Range (dB)	Step Size (dB)	Model No	1-4	5-9	10-24	25+	ROW
1 W	BNC Female	BNC Female	DC-500	Brass	DC-100: 1.1:1 100-300: 1.2:1 300-500: 1.3:1	0-65	1.0	PE7008-3	$966.55	$918.22	$869.90	$831.23	52

Step Attenuators, Toggle

75 Ohm

Max. Power (Watts)	Conn. Input	Conn. Output	Frequency Range (MHz)	Construction Material	VSWR Max. (MHz)	ATTN. Range (dB)	Step Size (dB)	Model No	1-4	5-9	10-24	25+	ROW
1 W	BNC Female	BNC Female	DC-1,000	Aluminum	1.3:1	0-42		PE70A1001	$758.06	$720.16	$682.25	$651.93	53
	F Female	F Female	0.3-1,000		1.37:1	0-71		PE70A1008	$827.56	$786.18	$744.80	$711.70	54

*** Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.**

See Our Website For Current Pricing & Real-Time Stock Availability!

Step Attenuators, Rotary

50 Ohm

Max. Power (Watts)	Conn. Input	Conn. Output	Frequency Range (MHz)	Construction Material	VSWR Max. (MHz)	ATTN. Range (dB)	Step Size (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
1 W	BNC Female	BNC Female	DC-1,000	Aluminum	1.2:1	0-1	0.1	PE7034-1	$650.25		See Web for Volume Pricing		55
					DC-1,000: 1.2:1	0-100	10.0	PE7034-2	$772.72				
2 W	BNC Female	BNC Female	DC-2,000	Aluminum	1.3:1	0-1	0.1	PE7034-6	$679.82				
			DC-2,200		DC-1,000: 1.2:1 1,000-2,200: 1.4:1	0-10	1.0	PE70A1024	$672.12				56
						0-70	10.0	PE70A1022	$862.16				57
	SMA Female	SMA Female				0-10	1.0	PE70A1025	$639.00				58
						0-70	10.0	PE70A1023	$690.74				59

75 Ohm

Max. Power (Watts)	Conn. Input	Conn. Output	Frequency Range (MHz)	Construction Material	VSWR Max. (MHz)	ATTN. Range (dB)	Step Size (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
1 W	BNC Female	BNC Female	DC-500	Aluminum	1.3:1	0-10	1.0	PE7035-2	$448.19		See Web for Volume Pricing		60
			DC-1,000		DC-500: 1.3:1 500-1,000: 1.4:1	0-1	0.1	PE7035-5	$1,015.96				

DC Bias Attenuators

50 Ohm

Max. Power (Watts)	Conn. Input	Conn. Output	Frequency Range (MHz)	Construction Material	VSWR Max.	Max. V (V)	Max. I (Amp)	ATTN. (dB)	Model No	1-9	10-24	25-49	50+	ROW
2 W	N Male	N Female	500-2,000	Passivated Stainless Steel	1.35:1	100	2	6	PE7062-6	$180.86	$171.82	$162.77	$155.54	61
								10	PE7062-10	$177.57	$168.69	$159.81	$152.71	
								20	PE7062-20	$152.31	$144.69	$137.08	$130.99	
	SMA Male	SMA Female						6	PE7061-6	$150.43	$142.91	$135.39	$129.37	62
								10	PE7061-10	$150.43	$142.91	$135.39	$129.37	
								20	PE7061-20	$163.20	$155.04	$146.88	$140.35	
	TNC Male	TNC Female						6	PE7063-6	$165.22	$156.96	$148.70	$142.09	63
								10	PE7063-10	$190.64	$181.11	$171.58	$163.95	
								20	PE7063-20	$190.64	$181.11	$171.58	$163.95	

75 Ohm

Max. Power (Watts)	Conn. Input	Conn. Output	Frequency Range (MHz)	Construction Material	VSWR Max.	Max. V (V)	Max. I (Amp)	ATTN. (dB)	Model No	1-9	10-24	25-49	50+	ROW
2 W	F Male	F Female	500-2,000	Brass	1.45:1	100	2	6	PE7064-6	$193.14	$183.48	$173.83	$166.10	64
								10	PE7064-10	$193.14	$183.48	$173.83	$166.10	
								20	PE7064-20	$190.29	$180.78	$171.26	$163.65	

See Our Website For Current Pricing & Real-Time Stock Availability!

Continuously Variable Attenuators

50 Ohm

Max. Power (Watts)	Conn. Input	Conn. Output	Frequency Range (MHz)	Construction Material	VSWR Max.	ATTN. (dB)	Model No	1	2-4	5-9	10+	ROW
5 W	SMA Female	SMA Female	DC-4,000		DC-1,000: 1.5:1 1,000-2,000: 1.6:1 2,000-3,000: 1.7:1 3,000-4,000: 1.8:1	5-95	PE7422	$1,731.32	$1,662.07	$1,592.81	$1,523.56	65

ACTIVE ATTENUATORS

TTL, USB, CMOS and Relay

Type	Frequency Range (GHz)	Atten. Range (dB)	IL (dB)	Step Resolu-tion (dB)	Switching Speed (µs)	Input/Output Connector	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
CMOS	DC - 13	0 - 31.5	5	0.5		SMA Female	PE70A5003	$4,956.42	See Web for Volume Pricing	66
Relay	DC - 1		1.5		6,000,000		PE70A8001	$925.30		67
	DC - 1	0 - 63	1.5	1			PE70A8000	$975.78		68
	DC - 1		2.2			F Female	PE70A8003	$1,796.30		69
	DC - 1	0 - 127	2.5				PE70A8004	$2,138.65		70
	DC - 1.5		3.2			SMA Female	PE70A8005	$2,326.58		71
	DC - 2	0 - 63.75	3.0	0.25			PE70A8002	$3,180.46		72
TTL	DC - 13	0 - 31.5	5.5	0.5	45		PE70A4000	$5,334.73		73
	5 MHz - 2.15	0 - 63	5.25	1	5,000	F Female	PE70A5012	$2,117.04		74
	30 MHz - 3	0 - 31.75	2.5	0.25	1,000	SMA Female	PE70A5004	$1,686.30		75
	30 MHz - 3	0 - 63	4	1			PE70A5006	$1,665.85		76
	30 MHz - 3	0 - 63.5	4	0.5			PE70A5005	$1,618.14		77
	30 MHz - 3	0 - 95	6	1			PE70A5007	$2,163.25		78
	30 MHz - 6	0 - 60	4	0.25	50,000		PE70A5000	$6,488.89		79
	100 MHz - 18	0 - 30	5	1	1	2.92mm Female	PE70A5001	$7,584.26		80
	100 MHz - 40		8				PE70A5002	$11,042.46		81
	200 MHz - 6	0 - 63	5.5		1,000	SMA Female	PE70A5009	$1,687.65		82
	200 MHz - 6	0 - 95	8				PE70A5010	$2,051.34		83
	450 MHz - 2.15	0 - 127	4.5		2,000	F Female	PE70A5011	$2,142.01		84
	500 MHz - 18	0 - 60	4.5	0.06	1	SMA Female	PE70A6000	$7,427.18		85
	700 MHz - 3	0 - 127	6	1	5,000		PE70A5008	$2,079.00		86
	18 - 40	0 - 30	6	0.03	1	2.4mm Female	PE70A6001	$8,147.25		87
USB	100 MHz - 18		5	1		SMA Female	PE70A3900	$4,506.94		88
	100 MHz - 40		5			2.92mm Female	PE70A3901	$6,128.09		89
	200 MHz - 6	0 - 95	8.3		4,000	SMA Female	PE70A3902	$2,163.25		90
Bench-Top TTL	200 MHz - 6		8		1,000		PE70A5013	$10,080.79		91

Variable Voltage Attenuators

Frequency Range (GHz)	Atten. Range (dB)	Insertion Loss (dB)	Switching Speed (µsec)	Input / Output Connectors	Model No	1	2-4	5-9	10+	ROW
DC - 20	0 - 30	2.5		SMA Female	PE70A1017	$8,851.71	$8,497.64	$8,143.57	$7,789.50	92
50 MHz - 2.2	0 - 20	3	50,000		PE70A1031	$1,439.67	$1,382.08	$1,324.50	$1,266.91	93
400 MHz - 6	0 - 40	4	10,000		PE70A1000	$6,759.53	$6,489.15	$6,218.77	$5,948.39	94
500 MHz - 18	0 - 60	4.5	3,000		PE70A2900	$6,738.50	$6,468.96	$6,199.42	$5,929.88	95
2 - 4		2	500		PE70A2000	$5,760.40	$5,529.98	$5,299.57	$5,069.15	96
4 - 8		2.5			PE70A2001	$6,750.45	$6,480.43	$6,210.41	$5,940.40	97

See Our Website For Current Pricing & Real-Time Stock Availability!

Variable Voltage Attenuators

Frequency Range (GHz)	Atten. Range (dB)	Insertion Loss (dB)	Switching Speed (µsec)	Input / Output Connectors	Model No	1	2-4	5-9	10+	ROW
6 - 12	0 - 60	2.8	500	SMA Female	PE70A2002	$7,083.10	$6,799.78	$6,516.45	$6,233.13	98
8 - 18		3.7			PE70A2003	$7,412.97	$7,116.45	$6,819.93	$6,523.41	99

EQUALIZERS

Positive Slope

Frequency Range (GHz)	Typ. Equalizing Value (dB)	Typ. Small Signal IL (dB)	Typ Input-Output VSWR	Max. RF Input Power (dBm)	In-Out Connectors (Field Replaceable)	Model No	1-4	5-9	10-24	25+	ROW
0.5 MHz - 2	2	1.4	1.8:1	+30	SMA Female	PE70A9000	$712.56	$676.93	$641.30	$612.80	1
	4	1				PE70A9001	$730.92	$694.37	$657.83	$628.59	2
	6	1.8				PE70A9002	$741.94	$704.84	$667.75	$638.07	3
1 - 18	4	1				PE70A9003	$1,270.84	$1,207.30	$1,143.76	$1,092.92	4
	6	1				PE70A9004	$1,270.84	$1,207.30	$1,143.76	$1,092.92	5
	8	1.5				PE70A9005	$1,270.84	$1,207.30	$1,143.76	$1,092.92	6
2 - 6	2	1				PE70A9006	$1,017.41	$966.54	$915.67	$874.97	7
	4	1.5				PE70A9007	$1,057.80	$1,004.91	$952.02	$909.71	8
2 - 12		1.5				PE70A9008	$1,017.41	$966.54	$915.67	$874.97	9
	8	1.5				PE70A9009	$1,101.88	$1,046.79	$991.69	$947.62	10
6 - 18	2	1.5				PE70A9010	$1,219.42	$1,158.45	$1,097.48	$1,048.70	11
	4	1.5				PE70A9011	$1,241.46	$1,179.39	$1,117.31	$1,067.66	12
	6	2				PE70A9012	$1,270.84	$1,207.30	$1,143.76	$1,092.92	13
	8	1.5				PE70A9013	$1,300.22	$1,235.21	$1,170.20	$1,118.19	14
18 - 40	2	2				PE70A9014	$1,425.10	$1,353.85	$1,282.59	$1,225.59	15
	4	2				PE70A9015	$1,458.16	$1,385.25	$1,312.34	$1,254.02	16
	6	2				PE70A9016	$1,483.87	$1,409.68	$1,335.48	$1,276.13	17
26.5 - 40	4	3				PE70A9017	$1,425.10	$1,353.85	$1,282.59	$1,225.59	18
	5	2.5				PE70A9018	$1,447.14	$1,374.78	$1,302.43	$1,244.54	19

BALUNS

Frequency Range (MHz)	Balanced Impedance (Ω)	Unbalanced Impedance (Ω)	Package	Model No	1-9	10-24	25-49	50+	ROW
20 - 520	25	50	Surface Mount	PE2BL1001	$260.75	$247.71	$234.68	$224.25	20
20 - 1,000				PE2BL1002	$252.30	$239.69	$227.07	$216.98	21
80 - 1,000				PE2BL1003	$231.27	$219.71	$208.14	$198.89	22
100 - 520				PE2BL1004	$252.30	$239.69	$227.07	$216.98	23
225 - 2,000				PE2BL1000	$245.48	$233.21	$220.93	$211.11	24
500 - 2,000				PE2BL1005	$232.78	$221.14	$209.50	$200.19	25
800 - 2,500				PE2BL1006	$287.41	$273.04	$258.67	$247.17	26

*** Bi-Dir is Bi-Directional. If No then Attenuator is Directional. Maximum power applies to input connector only.**

See Our Website For Current Pricing & Real-Time Stock Availability!

BIAS TEES AND DC BLOCKS

Bias Tees

Impedance	Frequency Range (MHz.)	Max. V (V)	Max. I (mA)	Connector	Bias Connector	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
50 Ohm	0.03 - 70,000	25	500	1.85mm	SMA	PE1619	$3,070.64	See Web for Volume Pricing	27
	0.03 - 85,000					PE1620	$3,302.70		28
	0.05 - 50,000	25	250	2.4mm	SMA	PE1610	$1,988.56		29
	10 - 40,000	16	250	2.92mm	Pin	PE1621	$1,256.86		39
	500 - 40,000	50	1000			PE1622	$1,485.42		45
	0.1 - 26,500	24	750	3.5mm	Solder Pin	PE1608	$1,309.36		32
	10 - 6,000	100	2500	N	Solder Pin	PE1612	$332.84		35
						PE1614	$456.27		36
						PE1616	$434.95		38
	250 - 2,500		7000			PE1618	$903.76		42
	0.1 - 12,400	24	750	SMA	Solder Pin	PE1606A	$689.00		30
	0.1 - 18,000					PE1BT1002	$731.06		31
	10 - 2,500	100	2500			PE1611	$369.24		33
	10 - 4,000					PE1613	$495.91		34
	10 - 6,000					PE1615	$343.74		37
	100 - 6,000	50	500			PE1604	$345.68		40
	250 - 2,500	100	7000			PE1617	$732.38		41
	400 - 10,000	50	200			PE1605	$537.57		43
	500 - 10,000	50	700		Pin	PE1BT1000	$1,038.96		44
	1,000 - 5,000	50	1000		Solder Pin	PE1603	$344.44		46

DC Blocks

Impedance	Connector	Frequency Range (MHz.)	Type	Max. V (V)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
50 Ohm	1.85mm	10 - 65,000	Inner		PE8258	$727.42	See Web for Volume Pricing	47
	2.4mm	100 - 50,000	Inner		PE8237	$1,527.39		48
			Inner/Outer		PE8239	$1,852.97		49
	2.92mm	10 - 26,500	Inner		PE8222	$302.25		50
			Outer	200	PE8223	$363.62		51
			Inner/Outer		PE8224	$490.46		52
		10 - 40,000	Inner		PE8225	$750.91		53
			Outer	200	PE8226	$1,554.18		54
			Inner/Outer		PE8227	$1,291.13		55
	BNC	10 - 4,000	Inner		PE8216	$204.06		56
			Outer		PE8217	$282.97		57
			Inner/Outer		PE8218	$320.51		58
	N	10 - 18,000	Inner		PE8213	$155.90		59
			Outer		PE8214	$245.57		60
			Inner/Outer		PE8215	$281.30		61
			Inner		PE8251	$208.30		62
	SMA		Inner		PE8210	$115.25		63
			Outer		PE8211	$181.68		64
			Inner/Outer		PE8212	$255.09		65
			Inner		PE8250	$155.86		66
	TNC		Inner		PE8219	$245.09		67
			Outer		PE8220	$345.08		68
			Inner/Outer		PE8221	$415.75		69
			Inner	950	PE8252	$315.57		70
75 Ohm	BNC	100 - 4,000	Inner		PE8231	$322.70		71
			Outer	200	PE8232	$194.07		72
			Inner/Outer		PE8233	$386.16		73
	F	10 - 2,000	Inner		PE8240	$134.26		74
			Inner/Outer		PE8242	$264.48		75
	N	100 - 4,000	Inner	200	PE8234	$276.50		76
			Inner/Outer		PE8236	$271.25		77

See Our Website For Current Pricing & Real-Time Stock Availability!

The Cable Creator™

Configure and Customize Your Cable Assemblies Online

Over 250,000 Custom Cable Configurations Available to Ship Same Day!

- Choose from over 2,030 RF coax connectors
- 123 coaxial cable types, including Twinax
- Choose your desired length (metric or standard)
- Includes high-reliability and low PIM assembly types
- ISO 9001:2015 certified production facility
- Optional Customizations:
  - Lead-free solder
  - Heat shrink
  - Labeling
  - Test plots
  - Clocking of right angle connectors

PE PASTERNACK
an INFINITE brand

Our Latest Cable Assembly Additions

Available in Standard and Custom Lengths! In-Stock and Shipped Same Day

High-Reliability Cable Assemblies

- MIL-DTL-17 and Temperature Conditioned, Low Loss Options
- Maximum Frequency Levels as High as 18 GHz
- J-STD Soldering Processes
- IPC/WHMA-A-620 Workmanship
- Lot Traceability for Cables, Connectors, Heat Shrink and Solder
- Detailed Test Reports and Plots

Low PIM Cable Assemblies

- Maximum PIM Levels as Low as -160dBc
- 100% PIM Tested with Results Marked on the Cable
- Low Loss, Excellent VSWR
- Lightweight, Extremely Flexible
- UL-Rated, Fire-Rated, Outdoor-Rated Cable Types
- Available with 4.3-10, 7/16 DIN, 4.1/9.5 Mini-DIN, Type-N, NEX10, SMA, and QMA Connector Series

40 GHz and 67 GHz Skew Matched Cable Pairs

- 1 ps Delay Match
- Excellent VSWR of 1.4:1
- 100% Tested Up to 40 or 67 GHz
- Extremely Flexible
- Polarity Indicators on Cable Ends

Handheld RF Analyzer Rugged Phase Stable Cable Assemblies

- VSWR as Low as 1.2:1
- Phase Stability with Flexure as Low as ± 1.5 Degrees
- Amplitude Stability with Flexure as Low as ± 0.1 dB
- Rugged Armor with 1200 PSI Crush Resistance, Protects Cable During Field Measurements
- UV Resistant Jacket
- Test Data Included with Each Serialized Cable

PE-P160LL Low Loss Cable Assemblies

- Triple-Shielded Low Loss Cable
- Maximum Frequency Levels as High as 18 GHz
- Shielding Effectivity >90 dB
- FEP Jacket
- 83% Phase Velocity
- Available with Type-N, SMA, and TNC Connector Series with Bulkhead and Right Angle Options

Coaxial Cable Assemblies Selection Guide

Do you need a cable assembly that isn't in our RF Product Guide?
Visit our website to view our entire selection of available assemblies or
to build your own custom length cable assembly!

3 Easy Ways to Find your Product.....

1. Search by PE Part Number

If you know the PE part number you are searching for, please reference our Part Number Index on Page 395

2. Quick Reference Guide

(Page number refers to first appearance of product in the Cable Assemblies Section)

Cable Connector	Page
1.0/2.3	97
1.0mm	97
1.85mm	97
1.85mm NMD	214
10-32	112
2.2-5	98
2.4mm	99
2.4mm NMD	214
2.92mm	100
2.92mm NMD	214
3.5mm	101
3.5mm NMD	215
4.1/9.5 Mini DIN	102
4.3-10	104

Cable Connector	Page
7/16 DIN	108
75 Ohm 1.6/5.6	216
75 Ohm BNC	217
75 Ohm F	218
75 Ohm Mini SMB	219
75 Ohm N	219
75 Ohm RCA	220
75 Ohm SMB	220
75 Ohm SMC	221
75 Ohm TNC	221
78 Ohm BNC Twinax	221
95 Ohm 3/4"-20 Twinax	221
Banana	221

Cable Connector	Page
BMA	113
BNC	118
C	125
D-Sub	215
FAKRA	125
FME	128
GR874	129
HMCX32 1.2	213
HN	129
LC	129
MC-Card	130
MCX	130
MHV	131
Mini SMP	132

Cable Connector	Page
Mini UHF	132
MMBX	132
MMCX	135
N	139
NEX10	214
NMO Mount	157
QMA	157
QN	158
Reverse Polarity SMA	179
Reverse Polarity TNC	209
Reverse Thread SMA	180
SC	158

Cable Connector	Page
SHV	159
SMA	159
SMB	195
SMC	198
SMP	201
SSMA	202
SSMB	202
SSMC	203
TNC	204
UHF	212
UMCX	213
UMCX 2.1	213
UMCX 2.5	213
WMCX 1.6	214

3. Cable Assembly Locator

(Cable Assembly Locator on Page 89-92 to locate the Cable Assembly you need by either connector end.)

SMA Female Bulkhead to MCX Plug Right Angle
PE39421-12

SMA FEMALE BULKHEAD TO:	EXAMPLE
MCX PLUG RIGHT ANGLE	23
MMCX PLUG RIGHT ANGLE	23
SMA FEMALE BULKHEAD	43
SMA MALE	17,23,31,32
SMA MALE RIGHT ANGLE	17,23,40,41
UMCX PLUG	76

MCX PLUG RIGHT ANGLE TO:	EXAMPLE
MCX PLUG	78
MCX PLUG RIGHT ANGLE	79
N FEMALE BULKHEAD	25
SMA FEMALE BULKHEAD	23
TNC FEMALE BULKHEAD	27
UMCX PLUG	76

The Cable Assembly Locator example above includes Between-Series Cable Assembly part numbers in two configurations: ***Connector 1 to Connector 2 as well as Connector 2 to Connector 1 will be found in the same location.***

Products can only be found under the first instance of the series combination. As an example, PE39421-12 above will be found in only one location in the Cable Assembly Section.

All Pasternack coaxial cable assembly part number indicate the length of the assembly (in inches) following the hyphen. Example: PE300-24 and PE300-26.5 are 24 inches and 26.5 inches in length respectively

NOTE: All cable assemblies have a length tolerance of 1.5% or ± 3/8", whichever is greater.

See Our Website For Current Pricing & Real-Time Stock Availability!

Cable Assembly Locator

Connector Type	Page
1.0/2.3 Jack Bulkhead To:	
1.0/2.3 JACK BULKHEAD	97
1.0/2.3 Plug To:	
BNC FEMALE BULKHEAD	97
1.0/2.3 Plug Right Angle To:	
BNC MALE	97
1.0mm Male To:	
1.0mm FEMALE	97
1.0mm MALE	97
1.85mm Female To:	
1.85mm FEMALE	98
1.85mm Male To:	
1.85mm FEMALE	97
1.85mm MALE	97
1.85mm MALE RIGHT ANGLE	97
2.4mm MALE	97
2.92mm MALE	98
1.85mm NMD Female To:	
1.85mm FEMALE	214
1.85mm MALE	214
10-32 Female To:	
BNC MALE	113
10-32 Male To:	
10-32 MALE	112
10-32 MALE RIGHT ANGLE	112
BNC MALE	113
10-32 Male Right Angle To:	
10-32 MALE RIGHT ANGLE	113
BNC FEMALE	113
SMP FEMALE	113
2.2-5 Female To:	
4.3-10 FEMALE	99
4.3-10 FEMALE BULKHEAD	99
4.3-10 MALE	99
4.3-10 MALE RIGHT ANGLE	99
N FEMALE	99
N FEMALE BULKHEAD	99
N MALE	99
N MALE RIGHT ANGLE	99
2.2-5 Male To:	
2.2-5 FEMALE	98
2.2-5 FEMALE BULKHEAD	98
2.2-5 MALE	98
2.2-5 MALE RIGHT ANGLE	98
4.3-10 FEMALE	98
4.3-10 FEMALE 4 HOLE FLANGE	98
4.3-10 FEMALE BULKHEAD	98
4.3-10 MALE	98
4.3-10 MALE RIGHT ANGLE	98
N FEMALE	98
N FEMALE BULKHEAD	98
N MALE	98
N MALE RIGHT ANGLE	98
2.2-5 Male Right Angle To:	
2.2-5 FEMALE	99
2.2-5 FEMALE BULKHEAD	99
2.2-5 MALE RIGHT ANGLE	99
2.4mm Female To:	
2.4mm FEMALE	100
2.4mm Female Bulkhead To:	
SMA MALE	100
2.4mm Male To:	
1.85mm MALE	99
2.4mm FEMALE	100
2.4mm MALE	99
2.4mm MALE RIGHT ANGLE	100
2.4mm NMD Female To:	
2.4mm FEMALE	214
2.4mm MALE	214

Connector Type	Page
2.92mm Female Bulkhead To:	
Straight Cut Lead Sexless	215
2.92mm Male To:	
1.85mm MALE	100
2.4mm MALE	100
2.92mm FEMALE	101
2.92mm FEMALE BULKHEAD	101
2.92mm MALE	100
2.92mm NMD Female To:	
2.92mm FEMALE	214
2.92mm MALE	214
3.5mm Female To:	
3.5mm FEMALE	102
3.5mm NMD FEMALE	215
Straight Cut Lead Sexless	215
3.5mm Male To:	
1.85mm MALE	101
3.5mm FEMALE	101
3.5mm FEMALE BULKHEAD	101
3.5mm MALE	101
3.5mm NMD Female To:	
3.5mm MALE	215
4.1/9.5 Mini DIN Female To:	
4.3-10 MALE	96
7/16 DIN MALE	96
N MALE	96
QMA MALE	96
SMA MALE	96
4.1/9.5 Mini DIN Male To:	
4.1/9.5 MINI DIN FEMALE	96
4.1/9.5 MINI DIN FEMALE BULKHEAD	102
4.1/9.5 MINI DIN MALE	96
4.1/9.5 MINI DIN MALE RIGHT ANGLE	102
4.3-10 FEMALE	96
4.3-10 MALE	96
7/16 DIN FEMALE	96
7/16 DIN MALE	96
N FEMALE	96
N MALE	96
QMA FEMALE	96
QMA MALE	96
QMA MALE RIGHT ANGLE	102
SMA FEMALE	96
SMA MALE	96
SMA MALE RIGHT ANGLE	103
4.1/9.5 Mini DIN Male Right Angle To:	
4.1/9.5 MINI DIN FEMALE	103
4.1/9.5 MINI DIN FEMALE BULKHEAD	103
4.1/9.5 MINI DIN MALE RIGHT ANGLE	103
4.3-10 FEMALE	103
4.3-10 MALE	103
7/16 DIN MALE	103
N MALE	103
N MALE RIGHT ANGLE	103
QMA MALE	103
SMA MALE	103
4.3-10 Female To:	
4.3-10 FEMALE	107
7/16 DIN MALE	96
7/16 DIN MALE RIGHT ANGLE	108
N MALE	96
N MALE RIGHT ANGLE	108
NEX10 MALE	108
QMA MALE	96
SMA MALE	96
4.3-10 Male To:	
4.3-10 FEMALE	96
4.3-10 FEMALE 4 HOLE FLANGE	105
4.3-10 FEMALE BULKHEAD	104
4.3-10 MALE	96
4.3-10 MALE RIGHT ANGLE	104
7/16 DIN FEMALE	96
7/16 DIN MALE	96
7/16 DIN MALE RIGHT ANGLE	105
N FEMALE	105

Connector Type	Page
N FEMALE BULKHEAD	106
N MALE	105
N MALE RIGHT ANGLE	105
NEX10 MALE	106
QMA FEMALE	96
QMA MALE	96
QMA MALE RIGHT ANGLE	106
SMA FEMALE	96
SMA MALE	96
SMA MALE RIGHT ANGLE	106
4.3-10 Male Right Angle To:	
4.3-10 FEMALE	106
4.3-10 FEMALE 4 HOLE FLANGE	107
4.3-10 FEMALE BULKHEAD	107
4.3-10 MALE	106
4.3-10 MALE RIGHT ANGLE	106
7/16 DIN FEMALE	107
7/16 DIN MALE	107
7/16 DIN MALE RIGHT ANGLE	107
N FEMALE BULKHEAD	107
N MALE	107
N MALE RIGHT ANGLE	107
NEX10 MALE	107
SMA MALE	107
SMA MALE RIGHT ANGLE	107
7/16 DIN Female To:	
7/16 DIN FEMALE	112
N MALE	96
N MALE RIGHT ANGLE	112
NEX10 MALE	112
QMA MALE	96
SMA MALE	96
7/16 DIN Male To:	
4.3-10 FEMALE	108
7/16 DIN FEMALE	96
7/16 DIN FEMALE BULKHEAD	110
7/16 DIN MALE	96
7/16 DIN MALE RIGHT ANGLE	109
N FEMALE	110
N FEMALE BULKHEAD	110
N MALE	110
N MALE RIGHT ANGLE	110
NEX10 MALE	111
QMA FEMALE	96
QMA MALE	96
QMA MALE RIGHT ANGLE	111
SC MALE	111
SMA FEMALE	96
SMA MALE	96
SMA MALE RIGHT ANGLE	111
7/16 DIN Male Right Angle To:	
7/16 DIN FEMALE	111
7/16 DIN FEMALE BULKHEAD	111
7/16 DIN MALE	111
7/16 DIN MALE RIGHT ANGLE	111
N FEMALE	112
N FEMALE BULKHEAD	112
N MALE	111
N MALE RIGHT ANGLE	112
NEX10 MALE	112
75 Ohm 1.6/5.6 Plug To:	
75 Ohm 1.6/5.6 PLUG	216
75 Ohm 1.6/5.6 PLUG RIGHT ANGLE	216
75 Ohm BNC MALE	216
75 Ohm 1.6/5.6 Plug Right Angle To:	
75 Ohm 1.6/5.6 PLUG RIGHT ANGLE	217
75 Ohm BNC Female To:	
75 Ohm BNC FEMALE	218
75 Ohm BNC Female Bulkhead To:	
75 Ohm BNC FEMALE BULKHEAD	218
75 Ohm BNC Male To:	
75 Ohm BNC FEMALE	217
75 Ohm BNC FEMALE BULKHEAD	217
75 Ohm BNC MALE	217
75 Ohm BNC MALE RIGHT ANGLE	217
Straight Cut Lead Sexless	221

Cable Assembly Locator

Connector Type	Page
75 Ohm BNC Male Right Angle To:	
75 Ohm BNC MALE RIGHT ANGLE	217
75 Ohm F Female To:	
75 Ohm F FEMALE	219
75 Ohm F Male To:	
75 Ohm BNC MALE	218
75 Ohm F FEMALE	218
75 Ohm F FEMALE BULKHEAD	219
75 Ohm F MALE	218
75 Ohm F MALE RIGHT ANGLE	218
75 Ohm Mini SMB Plug To:	
75 Ohm BNC MALE	219
75 Ohm MINI SMB JACK	219
75 Ohm MINI SMB PLUG	219
75 Ohm MINI SMB PLUG RIGHT ANGLE	219
75 Ohm TNC MALE	219
75 Ohm Mini SMB Plug Right Angle To:	
75 Ohm F FEMALE BULKHEAD	219
75 Ohm MINI SMB PLUG RIGHT ANGLE	219
75 Ohm N Female To:	
75 Ohm N FEMALE	220
75 Ohm N Male To:	
75 Ohm BNC MALE	219
75 Ohm F FEMALE	220
75 Ohm F MALE	220
75 Ohm N FEMALE	220
75 Ohm N MALE	220
75 Ohm RCA Male To:	
75 Ohm RCA FEMALE BULKHEAD	220
75 Ohm RCA MALE	220
75 Ohm RCA MALE RIGHT ANGLE	220
75 Ohm SMB Plug To:	
75 Ohm BNC MALE	220
75 Ohm SMB PLUG	221
75 Ohm SMC Plug To:	
75 Ohm BNC MALE	221
75 Ohm SMC PLUG	221
75 Ohm TNC Male To:	
75 Ohm BNC MALE	221
75 Ohm TNC MALE	221
78 Ohm BNC Twinax Plug To:	
78 Ohm BNC TWINAX PLUG	221
95 Ohm 3/4"-20 Twinax Male To:	
95 Ohm 3/4"-20 TWINAX MALE	221
Banana Plug To:	
SMA MALE	221
BMA Jack To:	
BMA JACK	115
BNC MALE	115
N MALE	116
SMA MALE	116
SMA MALE RIGHT ANGLE	116
SMP FEMALE	116
SMP FEMALE RIGHT ANGLE	116
TNC MALE	116
BMA Jack 2 Hole Flange To:	
BMA JACK 2 HOLE FLANGE	117
BNC MALE	117
N MALE	117
SMA MALE	117
SMA MALE RIGHT ANGLE	117
SMP FEMALE	117
SMP FEMALE RIGHT ANGLE	118
TNC MALE	118
BMA Jack Bulkhead To:	
BMA JACK BULKHEAD	117
BMA Jack Right Angle 2 Hole Flange To:	
BMA JACK RIGHT ANGLE 2 HOLE FLANGE	118

Connector Type	Page
BMA Plug Bulkhead To:	
BMA JACK	113
BMA JACK 2 HOLE FLANGE	114
BMA JACK BULKHEAD	113
BMA JACK RIGHT ANGLE 2 HOLE FLANGE	114
BMA PLUG BULKHEAD	113
BNC MALE	114
N MALE	114
SMA MALE	114
SMA MALE RIGHT ANGLE	115
SMP FEMALE	115
SMP FEMALE RIGHT ANGLE	115
TNC MALE	115
BNC Female To:	
BNC FEMALE	124
BNC MALE RIGHT ANGLE	124
NMO Mount Sexless	215
SMA MALE	125
BNC Female Bulkhead To:	
SMA MALE	125
BNC Male To:	
7/16 DIN FEMALE	121
BNC FEMALE	121
BNC FEMALE BULKHEAD	122
BNC MALE	93
BNC MALE RIGHT ANGLE	121
FAKRA PLUG	122
MCX JACK BULKHEAD	122
MHV MALE	122
N FEMALE	93
N FEMALE BULKHEAD	118
N MALE	93
N MALE RIGHT ANGLE	123
NMO Mount Sexless	215
SHV PLUG	123
SMA FEMALE	93
SMA FEMALE BULKHEAD	119
SMA MALE	93
SMA MALE RIGHT ANGLE	119
SSMC JACK BULKHEAD	123
SSMC PLUG	123
SSMC PLUG RIGHT ANGLE	123
Straight Cut Lead Sexless	215
TNC MALE	93
UHF FEMALE	123
BNC Male Right Angle To:	
BNC FEMALE BULKHEAD	124
BNC MALE RIGHT ANGLE	124
SMA FEMALE	124
TNC MALE RIGHT ANGLE	124
C Male To:	
C MALE	125
D-Subminiature Receptacle To:	
BNC MALE	215
FAKRA Jack To:	
FAKRA JACK	127
FAKRA JACK RIGHT ANGLE	128
MCX PLUG	128
REVERSE POLARITY TNC MALE	128
SMA FEMALE	128
FAKRA Jack Right Angle To:	
FAKRA PLUG	128
FAKRA Plug To:	
FAKRA JACK	126
FAKRA JACK RIGHT ANGLE	126
FAKRA PLUG	125
SMA MALE	127
FME Jack To:	
BNC MALE	128
FME JACK	128
NMO Mount Sexless	215
FME Plug To:	
BNC MALE	128
FME PLUG	128

Connector Type	Page
NMO Mount Sexless	215
FME Plug Bulkhead To:	
UMCX PLUG RIGHT ANGLE	128
GR874 Sexless To:	
BNC MALE	129
GR874 Sexless	129
HMCX32 1.2 Plug To:	
HMCX32 1.2 PLUG	213
HN Male To:	
7/16 DIN MALE RIGHT ANGLE	129
HN MALE	129
HN Male Right Angle To:	
HN FEMALE	129
LC Male To:	
LC MALE	129
LC Male Right Angle To:	
HN MALE	130
MC-Card Plug To:	
MC-Card PLUG	130
MC-Card PLUG RIGHT ANGLE	130
MC-Card Plug Right Angle To:	
MC-Card PLUG RIGHT ANGLE	130
MCX Jack To:	
MCX JACK	131
MCX Plug To:	
75 Ohm BNC MALE	215
BNC MALE	130
MCX PLUG	130
MCX PLUG RIGHT ANGLE	130
SMA MALE	130
TNC FEMALE BULKHEAD	131
MCX Plug Right Angle To:	
BNC FEMALE 4 HOLE FLANGE	131
MCX JACK BULKHEAD	131
MCX PLUG RIGHT ANGLE	131
SMA MALE	131
MHV Male To:	
MHV MALE	131
MHV MALE RIGHT ANGLE	132
SHV PLUG	132
Mini SMP Female To:	
MINI SMP FEMALE RIGHT ANGLE	132
SMA MALE RIGHT ANGLE	132
Mini UHF Female To:	
NMO Mount Sexless	215
Mini UHF Male To:	
MINI UHF MALE	132
NMO Mount Sexless	215
MMBX Plug To:	
MMBX PLUG	132
MMBX PLUG RIGHT ANGLE	133
N FEMALE BULKHEAD	133
REVERSE POLARITY SMA FEMALE BULKHEAD	134
SMA FEMALE	133
SMA FEMALE BULKHEAD	133
SMA MALE	133
SMA MALE RIGHT ANGLE	133
SSMB JACK BULKHEAD	134
TNC FEMALE BULKHEAD	134
MMBX Plug Right Angle To:	
MMBX PLUG RIGHT ANGLE	134
N FEMALE BULKHEAD	134
REVERSE POLARITY SMA FEMALE BULKHEAD	135
SMA FEMALE	135
SMA FEMALE BULKHEAD	135
SMA MALE	134
SMA MALE RIGHT ANGLE	134
TNC FEMALE BULKHEAD	135

Cable Assembly Locator

Connector Type	Page
MMCX Plug To:	
MMCX PLUG	135
MMCX PLUG RIGHT ANGLE	135
N FEMALE BULKHEAD	136
SMC PLUG	136
MMCX Plug Right Angle To:	
BNC FEMALE BULKHEAD	136
MMCX PLUG	136
SMA FEMALE	136
SMA MALE RIGHT ANGLE	136
N Female To:	
7/16 DIN MALE	96
N FEMALE	93
N FEMALE BULKHEAD	152
N MALE	94
NEX10 MALE	154
NMO Mount Sexless	215
QN MALE	154
QN MALE RIGHT ANGLE	154
SMA MALE	93
SMA MALE RIGHT ANGLE	153
TNC MALE	93
N Female 4 Hole Flange To:	
MMCX PLUG RIGHT ANGLE	157
N MALE RIGHT ANGLE	157
N Female Bulkhead To:	
HMCX32 1.2 PLUG	156
MCX PLUG RIGHT ANGLE	155
MMCX PLUG RIGHT ANGLE	155
N FEMALE BULKHEAD	154
N MALE	155
N MALE RIGHT ANGLE	155
NEX10 MALE	157
QMA MALE RIGHT ANGLE	155
REVERSE POLARITY SMA MALE RIGHT ANGLE	156
SMA FEMALE	156
SMA FEMALE BULKHEAD	156
SMA MALE	154
SMA MALE RIGHT ANGLE	154
SMP FEMALE RIGHT ANGLE	156
TNC FEMALE BULKHEAD	156
TNC MALE	155
TNC MALE RIGHT ANGLE	156
UMCX 2.1 PLUG	156
UMCX 2.5 PLUG	156
WMCX 1.6 PLUG	156
N Male To:	
4.1/9.5 MINI DIN MALE	96
4.3-10 MALE	96
7/16 DIN FEMALE	96
7/16 DIN MALE	96
7/16 DIN MALE RIGHT ANGLE	144
BNC FEMALE BULKHEAD	145
BNC MALE	144
BNC MALE RIGHT ANGLE	145
C FEMALE	145
GR874 Sexless	145
MCX PLUG RIGHT ANGLE	145
MINI UHF MALE	145
N FEMALE	93
N FEMALE 4 HOLE FLANGE	143
N FEMALE BULKHEAD	142
N MALE	93
N MALE RIGHT ANGLE	139
NEX10 MALE	149
NMO Mount Sexless	215
QMA FEMALE	96
QMA MALE	96
QMA MALE RIGHT ANGLE	145
QN MALE	146
QN MALE RIGHT ANGLE	146
REVERSE POLARITY TNC MALE	149
REVERSE POLARITY TNC MALE RIGHT ANGLE	149
SHV PLUG	146
SMA FEMALE	96
SMA FEMALE BULKHEAD	147
SMA MALE	93
SMA MALE RIGHT ANGLE	147

Connector Type	Page
SSMC JACK BULKHEAD	147
SSMC PLUG	147
SSMC PLUG RIGHT ANGLE	147
TNC FEMALE	149
TNC FEMALE BULKHEAD	149
TNC MALE	93
TNC MALE RIGHT ANGLE	149
UMCX PLUG RIGHT ANGLE	149
N Male Right Angle To:	
BNC MALE	149
BNC MALE RIGHT ANGLE	149
N FEMALE	151
N FEMALE BULKHEAD	151
N MALE	150
N MALE RIGHT ANGLE	150
NEX10 MALE	152
SMA FEMALE BULKHEAD	152
SMA MALE	152
SMA MALE RIGHT ANGLE	152
TNC FEMALE BULKHEAD	152
TNC MALE	152
TNC MALE RIGHT ANGLE	152
UHF MALE	152
NEX10 Male To:	
NEX10 FEMALE	214
NEX10 FEMALE BULKHEAD	214
NEX10 MALE	214
NEX10 MALE RIGHT ANGLE	214
NEX10 Male Right Angle To:	
NEX10 FEMALE	214
NEX10 FEMALE BULKHEAD	214
NEX10 MALE RIGHT ANGLE	214
NMO Mount Sexless To:	
TNC MALE	157
QMA Female To:	
SMA MALE	96
QMA Male To:	
QMA FEMALE	96
QMA FEMALE BULKHEAD	157
QMA MALE	96
QMA MALE RIGHT ANGLE	157
SMA FEMALE	96
SMA MALE	96
SMA MALE RIGHT ANGLE	157
QMA Male Right Angle To:	
QMA FEMALE	158
QMA FEMALE BULKHEAD	158
QMA MALE RIGHT ANGLE	157
SMA MALE	158
QN Male To:	
QN MALE	158
QN MALE RIGHT ANGLE	158
QN Male Right Angle To:	
N FEMALE	158
Reverse Polarity SMA Female Bulkhead To:	
HMCX32 1.2 PLUG	194
SMA MALE	194
SMA MALE RIGHT ANGLE	194
UMCX 2.1 PLUG	194
UMCX 2.5 PLUG	194
UMCX PLUG RIGHT ANGLE	194
WMCX 1.6 PLUG	195
Reverse Polarity SMA Male To:	
BNC MALE	179
MCX PLUG RIGHT ANGLE	179
N FEMALE BULKHEAD	179
N MALE	179
REVERSE POLARITY SMA FEMALE	180
REVERSE POLARITY SMA MALE	179
TNC MALE	180
Reverse Polarity SMA Male Right Angle To:	
N MALE	187
N MALE RIGHT ANGLE	187

Connector Type	Page
SMA MALE	187
Reverse Polarity TNC Female To:	
REVERSE POLARITY SMA MALE	210
Reverse Polarity TNC Female Bulkhead To:	
MMCX PLUG	212
REVERSE POLARITY SMA MALE	212
REVERSE POLARITY TNC MALE	212
SSMC PLUG RIGHT ANGLE	212
UMCX PLUG	212
Reverse Polarity TNC Male To:	
BNC MALE	209
Reverse Thread SMA Female Bulkhead To:	
UMCX PLUG RIGHT ANGLE	195
Reverse Thread SMA Male To:	
Reverse Thread SMA MALE	180
SC Male To:	
SC MALE	158
SHV Jack Bulkhead To:	
SHV PLUG	159
SHV Plug To:	
SHV JACK BULKHEAD	159
SHV PLUG	159
SMA Female To:	
FAKRA JACK	188
FAKRA PLUG	187
MCX PLUG RIGHT ANGLE	188
MMCX PLUG	188
N FEMALE	94
N FEMALE BULKHEAD	189
N MALE	94
N MALE RIGHT ANGLE	189
NMO Mount Sexless	216
QMA MALE	189
SMA FEMALE	94
SMA FEMALE BULKHEAD	190
SMA MALE	94
SMA MALE RIGHT ANGLE	189
SSMC JACK BULKHEAD	190
SSMC PLUG	190
SSMC PLUG RIGHT ANGLE	190
Straight Cut Lead Sexless	216
TNC FEMALE	94
TNC FEMALE BULKHEAD	190
TNC MALE	94
TNC MALE RIGHT ANGLE	190
Trimmed Lead Sexless	216
SMA Female 2 Hole Flange To:	
SMA FEMALE 2 HOLE FLANGE	195
SMP FEMALE	195
SMP FEMALE RIGHT ANGLE	195
SMA Female 4 Hole Flange To:	
MMCX PLUG RIGHT ANGLE	195
SMA FEMALE 4 HOLE FLANGE	195
SMA Female Bulkhead To:	
HMCX32 1.2 PLUG	194
MCX PLUG RIGHT ANGLE	191
MMCX PLUG	191
MMCX PLUG RIGHT ANGLE	191
N FEMALE BULKHEAD	191
N MALE	191
N MALE RIGHT ANGLE	191
REVERSE POLARITY SMA MALE	193
SMA FEMALE	192
SMA FEMALE BULKHEAD	191
SMA MALE	191
SMA MALE RIGHT ANGLE	192
SMB PLUG RIGHT ANGLE	193
SMP FEMALE	193
SMP FEMALE RIGHT ANGLE	193
SSMC JACK BULKHEAD	193
SSMC PLUG	193
SSMC PLUG RIGHT ANGLE	193
TNC FEMALE BULKHEAD	194

Cable Assembly Locator

Connector Type	Page
SMA Female Bulkhead To:	
TNC MALE	191
TNC MALE RIGHT ANGLE	193
UMCX 2.1 PLUG	194
UMCX 2.5 PLUG	194
UMCX PLUG RIGHT ANGLE	194
WMCX 1.6 PLUG	194
SMA Female Right Angle To:	
SMA FEMALE BULKHEAD	190
SMA Male To:	
1.85mm MALE	159
2.4mm MALE	159
2.92mm MALE	160
7/16 DIN MALE	96
BNC MALE	160
BNC MALE RIGHT ANGLE	161
FAKRA JACK	161
FAKRA PLUG	161
HMCX32 1.2 PLUG	178
MC-Card PLUG	162
MCX PLUG	162
MINI UHF MALE	162
MMCX PLUG	162
MMCX PLUG RIGHT ANGLE	163
N FEMALE	94
N FEMALE BULKHEAD	164
N MALE	94
N MALE RIGHT ANGLE	164
NEX10 MALE	179
NMO Mount Sexless	215
QMA MALE	166
REVERSE POLARITY SMA MALE	173
REVERSE POLARITY SMA MALE RIGHT ANGLE	173
REVERSE POLARITY TNC MALE	178
Reverse Thread SMA MALE	173
SMA FEMALE	94
SMA FEMALE BULKHEAD	170
SMA MALE	94
SMA MALE RIGHT ANGLE	168
SMB JACK	174
SMB PLUG	174
SMB PLUG RIGHT ANGLE	174
SMC PLUG	174
SMP FEMALE	175
SMP FEMALE RIGHT ANGLE	175
SSMA MALE	175
SSMC JACK	176
SSMC JACK BULKHEAD	176
SSMC PLUG	175
SSMC PLUG RIGHT ANGLE	175
Straight Cut Lead Sexless	216
TNC FEMALE	94
TNC FEMALE BULKHEAD	178
TNC MALE	94
TNC MALE RIGHT ANGLE	177
UMCX 2.1 PLUG	178
UMCX 2.5 PLUG	178
UMCX PLUG	178
WMCX 1.6 PLUG	179
SMA Male Right Angle To:	
BNC FEMALE BULKHEAD	181
BNC MALE	181
MCX JACK	181
MCX PLUG RIGHT ANGLE	181
MMCX PLUG RIGHT ANGLE	181
N FEMALE	182
N FEMALE BULKHEAD	182
N MALE	181
N MALE RIGHT ANGLE	182
NEX10 MALE	187
REVERSE POLARITY SMA FEMALE	185
REVERSE POLARITY SMA MALE RIGHT ANGLE	185
REVERSE POLARITY TNC MALE RIGHT ANGLE	187
SMA FEMALE	184
SMA FEMALE BULKHEAD	180
SMA MALE	182
SMA MALE RIGHT ANGLE	180
SMB PLUG	185
SMB PLUG RIGHT ANGLE	185
SMC PLUG RIGHT ANGLE	186

Connector Type	Page
SSMC JACK BULKHEAD	186
SSMC PLUG	186
SSMC PLUG RIGHT ANGLE	186
TNC FEMALE BULKHEAD	186
TNC MALE	180
TNC MALE RIGHT ANGLE	186
SMB Plug To:	
BNC MALE	195
N FEMALE	196
SMB JACK BULKHEAD	197
SMB PLUG	196
SMB PLUG RIGHT ANGLE	196
SMP FEMALE	197
SSMA MALE	197
SMB Plug Right Angle To:	
BNC MALE	197
SMA MALE	197
SMB JACK BULKHEAD	198
SMB PLUG RIGHT ANGLE	197
SSMB PLUG	198
SMC Jack Bulkhead To:	
UMCX PLUG RIGHT ANGLE	201
SMC Plug To:	
10-32 MALE RIGHT ANGLE	198
BNC MALE	198
MCX PLUG	198
SMA MALE	198
SMC JACK BULKHEAD	199
SMC PLUG	198
SMC PLUG RIGHT ANGLE	199
SMC Plug Right Angle To:	
BNC MALE	200
SMC JACK BULKHEAD	200
SMC PLUG RIGHT ANGLE	200
TNC FEMALE BULKHEAD	200
SMP Female To:	
SMA MALE	201
SMP FEMALE	201
SMP FEMALE RIGHT ANGLE	201
SMP Female Right Angle To:	
BNC MALE	201
MMCX PLUG RIGHT ANGLE	201
N FEMALE BULKHEAD	201
REVERSE POLARITY TNC FEMALE BULKHEAD	202
SMA FEMALE	201
SMA FEMALE 2 HOLE FLANGE	202
SMA MALE RIGHT ANGLE	201
SMP FEMALE	202
SMP FEMALE RIGHT ANGLE	202
SMP Male Bulkhead To:	
SMA MALE	201
SMP FEMALE RIGHT ANGLE	201
SSMA Male To:	
SSMA MALE	202
SSMA MALE RIGHT ANGLE	202
Trimmed Lead Sexless	216
SSMA Male Right Angle To:	
SSMA MALE RIGHT ANGLE	202
SSMB Plug To:	
SMA MALE	202
SSMB PLUG	202
SSMB Plug Right Angle To:	
SSMB PLUG RIGHT ANGLE	203
Straight Cut Lead Sexless	216
SSMC Jack Bulkhead To:	
SSMC JACK BULKHEAD	204
SSMC JACK RIGHT ANGLE BULKHEAD	204
TNC MALE	204
SSMC Jack Right Angle Bulkhead To:	
SSMC JACK RIGHT ANGLE BULKHEAD	204
SSMC Plug To:	
SMB JACK BULKHEAD	203

Connector Type	Page
SSMC JACK BULKHEAD	203
SSMC JACK RIGHT ANGLE BULKHEAD	203
SSMC PLUG	203
SSMC PLUG RIGHT ANGLE	203
TNC MALE	203
SSMC Plug Right Angle To:	
SMA MALE	203
SSMC JACK BULKHEAD	204
SSMC JACK RIGHT ANGLE BULKHEAD	204
SSMC PLUG RIGHT ANGLE	203
TNC FEMALE BULKHEAD	204
TNC MALE	204
TNC Female To:	
N FEMALE	95
N MALE	95
NMO Mount Sexless	216
REVERSE POLARITY TNC MALE	210
SMA MALE	210
TNC FEMALE	95
TNC MALE	95
TNC Female Bulkhead To:	
MCX PLUG RIGHT ANGLE	210
MMCX PLUG RIGHT ANGLE	210
N FEMALE BULKHEAD	211
N MALE	211
N MALE RIGHT ANGLE	211
SMA MALE	211
SMA MALE RIGHT ANGLE	211
SMC PLUG RIGHT ANGLE	211
SMP FEMALE RIGHT ANGLE	211
SSMC PLUG RIGHT ANGLE	211
TNC FEMALE BULKHEAD	211
TNC MALE	211
TNC MALE RIGHT ANGLE	211
UMCX PLUG RIGHT ANGLE	212
TNC Male To:	
BNC MALE	204
MINI UHF MALE	205
N FEMALE	95
N FEMALE BULKHEAD	205
N MALE	95
N MALE RIGHT ANGLE	205
REVERSE POLARITY TNC MALE	208
SMA MALE	206
SMA MALE RIGHT ANGLE	206
SMP FEMALE RIGHT ANGLE	206
TNC FEMALE	95
TNC FEMALE BULKHEAD	208
TNC MALE	94
TNC MALE RIGHT ANGLE	208
TNC Male Right Angle To:	
N FEMALE BULKHEAD	209
N MALE	209
N MALE RIGHT ANGLE	209
TNC FEMALE	210
TNC FEMALE BULKHEAD	210
TNC MALE	209
TNC MALE RIGHT ANGLE	209
UHF Male To:	
BNC MALE	212
UHF MALE	213
UMCX 2.1 Plug To:	
UMCX 2.1 PLUG	213
UMCX 2.5 Plug To:	
UMCX 2.5 PLUG	213
UMCX Plug Right Angle To:	
MCX JACK BULKHEAD	213
MCX PLUG	213
MCX PLUG RIGHT ANGLE	213
MMCX PLUG RIGHT ANGLE	213
REVERSE POLARITY MCX JACK BULKHEAD	213
SSMB PLUG	213
Straight Cut Lead Sexless	216
WMCX 1.6 Plug To:	
WMCX 1.6 PLUG	214

HIGH-RELIABILITY RF CABLE ASSEMBLIES

Product Features

- Max. Frequency as High as 18 GHz
- Double and Triple Shielded Versions
- Lot Traceability
- J-STD-Soldering
- High-Reliability Cable and Connectors
- RF Test Plots
- Detailed Test Report
- In-Stock and Shipped Same Day

Applications

- Hi-Rel
- MIL-DTL-17 Requirements
- Avionics
- IFF
- SATCOM
- ECM

MIL-DTL-17 Cable Assembly Series

Temperature Conditioned, Low Loss Cable Assembly Series

Pasternack's MIL-DTL-17 Cable Assemblies and Temperature-Conditioned, Low-Loss Cable Assemblies are part of a full line of high-reliability RF components that are in-stock and available for shipment same day. These Commercial-Off-The-Shelf (COTS) assemblies offer a combination of superior materials, processes, and acceptance testing designed to ensure rugged, highly reliable performance for your mission critical applications.

Each assembly is manufactured using J-STD soldering processes and WHMA-A-620 workmanship and is also traceable to its component lots for every material used (RF connectors, coax cable, heat shrink, and solder). There is 100% test sampling of assemblies for connector gaging, insertion loss, VSWR, DWV, workmanship, configuration, and marking, with sampled (AQL) inspections performed for length and mass. A detailed test report accompanies each assembled lot.

Whether the need is to provide a high-reliablity MIL-SPEC connection or a rugged, dependable cable assembly, Pasternack has the right assembly for the job. Visit us online at www.pasternack.com to configure and customize your order, or sign up for our mailing list to receive the latest news and product information.

MIL-DTL-17 BNC CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
M17/28-RG058						
PE3M0115	M17/28-RG058	65.9	BNC, Male	BNC, Male	1	1
PE3M0116				SMA, Male		2
PE3M0117				SMA, Male, RA		3
PE3M0118				TNC, Male		4
M17/60-RG142						
PE3M0001	M17/60-RG142	69.5	BNC, Male	BNC, Male	4	5
PE3M0002				N, Male		6
PE3M0003				N, Female		7
PE3M0004						8
PE3M0005				SMA, Male		9
PE3M0006				SMA, Male, RA		10
PE3M0007				TNC, Male		11
M17/84-RG223						
PE3M0029	M17/84-RG223	65.9	BNC, Male	BNC, Male	4	12
PE3M0030				N, Male		13
PE3M0031				N, Female		14
PE3M0032						15
PE3M0033				SMA, Male		16
PE3M0034				SMA, Male, RA		17
PE3M0035				TNC, Male		18
M17/113-RG316						
PE3M0085	M17/113-RG316	69.5	BNC, Male	BNC, Male	3	19
PE3M0086				SMA, Male		20
PE3M0087				SMA, Male, RA		21
PE3M0088				SMA, Female		22
PE3M0089				TNC, Male		23
M17/119-RG174						
PE3M0100	M17/119-RG174	65.9	BNC, Male	BNC, Male	1	24
PE3M0101				SMA, Male		25
PE3M0102				SMA, Male, RA		26
PE3M0103				SMA, Female		27
PE3M0104				TNC, Male		28
M17/128-RG400						
PE3M0057	M17/128-RG400	69.5	BNC, Male	BNC, Male	4	29
PE3M0058				N, Male		30
PE3M0059				N, Female		31
PE3M0060						32
PE3M0061				SMA, Male		33
PE3M0062				SMA, Male, RA		34
PE3M0063				TNC, Male		35

MIL-DTL-17 N TYPE CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
M17/60-RG142						
PE3M0008	M17/60-RG142	69.5	N, Male	N, Male	11	36
PE3M0009				N, Female		37
PE3M0010						38
PE3M0014				SMA, Male		39
PE3M0015				SMA, Male, RA		40
PE3M0016				TNC, Male		41
PE3M0011			N, Female	N, Female		42
PE3M0012						43
PE3M0013						44
PE3M0017				SMA, Male		45
PE3M0020						46
PE3M0018				SMA, Male, RA		47
PE3M0021						48
PE3M0019				TNC, Male		49
PE3M0022						50
M17/84-RG223						
PE3M0036	M17/84-RG223	65.9	N, Male	N, Male	11	51
PE3M0037				N, Female		52
PE3M0038						53
PE3M0042				SMA, Male		54
PE3M0043				SMA, Male, RA		55
PE3M0044				TNC, Male		56
PE3M0039			N, Female	N, Female		57
PE3M0040						58
PE3M0041						59
PE3M0045				SMA, Male		60
PE3M0048						61
PE3M0046				SMA, Male, RA		62
PE3M0049						63
PE3M0047				TNC, Male		64
PE3M0050						65
M17/128-RG400						
PE3M0064	M17/128-RG400	69.5	N, Male	N, Male	11	66
PE3M0065				N, Female		67
PE3M0066						68
PE3M0070				SMA, Male		69
PE3M0071				SMA, Male, RA		70
PE3M0072				TNC, Male		71
PE3M0067			N, Female	N, Female		72
PE3M0068						73

See Our Website For Current Pricing & Real-Time Stock Availability!

MIL-DTL-17 N TYPE CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
M17/128-RG400						
PE3M0069	M17/128-RG400	69.5	N, Female	N, Female	11	74
PE3M0073				SMA, Male		75
PE3M0076						76
PE3M0074				SMA, Male, RA		77
PE3M0077						78
PE3M0075				TNC, Male		79
PE3M0078						80

MIL-DTL-17 SMA CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
M17/28-RG058						
PE3M0119	M17/28-RG058	65.9	SMA, Male	SMA, Male	1	81
PE3M0120				SMA, Male, RA		82
PE3M0122				TNC, Male		83
PE3M0121			SMA, Male, RA	SMA, Male, RA		84
PE3M0123				TNC, Male		85
M17/60-RG142						
PE3M0023	M17/60-RG142	69.5	SMA, Male	SMA, Male	12.4	86
PE3M0024				SMA, Male, RA		87
PE3M0026				TNC, Male	11	88
PE3M0025			SMA, Male, RA	SMA, Male, RA	12.4	89
PE3M0027				TNC, Male	11	90
M17/84-RG223						
PE3M0051	M17/84-RG223	65.9	SMA, Male	SMA, Male	12.4	91
PE3M0052				SMA, Male, RA		92
PE3M0054				TNC, Male	11	93
PE3M0053			SMA, Male, RA	SMA, Male, RA	12.4	94
PE3M0055				TNC, Male	11	95
M17/113-RG316						
PE3M0090	M17/113-RG316	69.5	SMA, Male	SMA, Male	3	96
PE3M0091				SMA, Male, RA		97
PE3M0092				SMA, Female		98
PE3M0096				TNC, Male		99
PE3M0093			SMA, Male, RA	SMA, Male, RA		1
PE3M0094				SMA, Female		2
PE3M0097				TNC, Male		3
PE3M0095			SMA, Female	SMA, Female		4
PE3M0098				TNC, Male		5
M17/119-RG174						
PE3M0105	M17/119-RG174	65.9	SMA, Male	SMA, Male	1	6
PE3M0106				SMA, Male, RA		7
PE3M0107				SMA, Female		8
PE3M0111				TNC, Male		9
PE3M0108			SMA, Male, RA	SMA, Male, RA		10
PE3M0109				SMA, Female		11
PE3M0112				TNC, Male		12
PE3M0110			SMA, Female	SMA, Female		13
PE3M0113				TNC, Male		14
M17/128-RG400						
PE3M0079	M17/128-RG400	69.5	SMA, Male	SMA, Male	12.4	15
PE3M0080				SMA, Male, RA		16
PE3M0082				TNC, Male	11	17
PE3M0081			SMA, Male, RA	SMA, Male, RA	12.4	18
PE3M0083				TNC, Male	11	19

MIL-DTL-17 TNC CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
M17/28-RG058						
PE3M0124	M17/28-RG058	65.9	TNC, Male	TNC, Male	1	20
M17/60-RG142						
PE3M0028	M17/60-RG142	69.5	TNC, Male	TNC, Male	11	21
M17/84-RG223						
PE3M0056	M17/84-RG223	65.9	TNC, Male	TNC, Male	11	22
M17/113-RG316						
PE3M0099	M17/113-RG316	69.5	TNC, Male	TNC, Male	3	23
M17/119-RG174						
PE3M0114	M17/119-RG174	65.9	TNC, Male	TNC, Male	1	24
M17/128-RG400						
PE3M0084	M17/128-RG400	69.5	TNC, Male	TNC, Male	11	25

TEMPERATURE CONDITIONED, LOW LOSS N TYPE CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
PE-P142LL						
PE3M0174	PE-P142LL	80	N, Male	N, Male	18	26
PE3M0176				N, Male, RA		27
PE3M0175				N, Female		28
PE3M0179			N, Male, RA	N, Male, RA		29
PE3M0178			N, Female			30
PE3M0177				N, Female		31
PE-P160LL						
PE3M0219	PE-P160LL	82.5	N, Male	N, Male	18	32
PE3M0221				N, Male, RA		33
PE3M0220				N, Female		34
PE3M0224			N, Male, RA	N, Male, RA		35
PE3M0223			N, Female			36
PE3M0222				N, Female		37
PE-P300LL						
PE3M0247	PE-P300LL	83	N, Male	N, Male	18	38
PE3M0249				N, Male, RA		39
PE3M0248				N, Female		40
PE3M0252			N, Male, RA	N, Male, RA		41
PE3M0251			N, Female			42
PE3M0250				N, Female		43

TEMPERATURE CONDITIONED, LOW LOSS SMA CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
PE-P142LL						
PE3M0132	PE-P142LL	80	SMA, Male	N, Male	18	44
PE3M0134				N, Male, RA		45
PE3M0133				N, Female		46
PE3M0125				SMA, Male		47
PE3M0128				SMA, Male, RA		48
PE3M0126				SMA, Female		49
PE3M0127						50
PE3M0129				TNC, Male		51
PE3M0131				TNC, Male, RA		52
PE3M0130				TNC, Female		53
PE3M0156			SMA, Male, RA	N, Male		54
PE3M0158				N, Male, RA		55
PE3M0157				N, Female		56
PE3M0152				SMA, Male, RA		57
PE3M0153				TNC, Male		58
PE3M0155				TNC, Male, RA		59
PE3M0154				TNC, Female		60
PE3M0141			SMA, Female	N, Male		61
PE3M0149						62
PE3M0143				N, Male, RA		63
PE3M0151						64
PE3M0142				N, Female		65
PE3M0150						66
PE3M0137				SMA, Male, RA		67
PE3M0145						68
PE3M0135				SMA, Female		69
PE3M0136						70
PE3M0144						71
PE3M0138				TNC, Male		72
PE3M0146						73
PE3M0140				TNC, Male, RA		74
PE3M0148						75
PE3M0139				TNC, Female		76
PE3M0147						77
PE-P160LL						
PE3M0186	PE-P160LL	82.5	SMA, Male	N, Male	18	78
PE3M0188				N, Male, RA		79
PE3M0187				N, Female		80

Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

For our complete selection of cable assemblies, please visit our website

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
PE-P160LL						
PE3M0180	PE-P160LL	82.5	SMA, Male	SMA, Male	18	81
PE3M0182				SMA, Male, RA		82
PE3M0181				SMA, Female		83
PE3M0183				TNC, Male		84
PE3M0185				TNC, Male, RA		85
PE3M0184				TNC, Female		86
PE3M0201			SMA, Male, RA	N, Male		87
PE3M0203				N, Male, RA		88
PE3M0202				N, Female		89
PE3M0197				SMA, Male, RA		90
PE3M0198				TNC, Male		91
PE3M0200				TNC, Male, RA		92
PE3M0199				TNC, Female		93
PE3M0194			SMA, Female	N, Male		94
PE3M0196				N, Male, RA		95
PE3M0195				N, Female		96
PE3M0190				SMA, Male, RA		97
PE3M0189				SMA, Female		98
PE3M0191				TNC, Male		99
PE3M0193				TNC, Male, RA		1
PE3M0192				TNC, Female		2
PE-P300LL						
PE3M0229	PE-P300LL	83	SMA, Male	N, Male	18	3
PE3M0231				N, Male, RA		4
PE3M0230				N, Female		5
PE3M0225				SMA, Male		6
PE3M0226				SMA, Male, RA		7
PE3M0227				TNC, Male		8
PE3M0228				TNC, Male, RA		9
PE3M0235			SMA, Male, RA	N, Male		10
PE3M0237				N, Male, RA		11
PE3M0236				N, Female		12
PE3M0232				SMA, Male, RA		13
PE3M0233				TNC, Male		14
PE3M0234				TNC, Male, RA		15

TEMPERATURE CONDITIONED, LOW LOSS TNC CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
PE-P142LL						
PE3M0162	PE-P142LL	80	TNC, Male	N, Male	18	16

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Frequency Max. (GHz)	ROW
PE-P142LL						
PE3M0164	PE-P142LL	80	TNC, Male	N, Male, RA	18	17
PE3M0163				N, Female		18
PE3M0159				TNC, Male		19
PE3M0161				TNC, Male, RA		20
PE3M0160				TNC, Female		21
PE3M0171			TNC, Male, RA	N, Male		22
PE3M0173				N, Male, RA		23
PE3M0172				N, Female		24
PE3M0170				TNC, Male, RA		25
PE3M0167			TNC, Female	N, Male		26
PE3M0169				N, Male, RA		27
PE3M0168				N, Female		28
PE3M0166				TNC, Male, RA		29
PE3M0165				TNC, Female		30
PE-P160LL						
PE3M0207	PE-P160LL	82.5	TNC, Male	N, Male	18	31
PE3M0209				N, Male, RA		32
PE3M0208				N, Female		33
PE3M0204				TNC, Male		34
PE3M0206				TNC, Male, RA		35
PE3M0205				TNC, Female		36
PE3M0216			TNC, Male, RA	N, Male		37
PE3M0218				N, Male, RA		38
PE3M0217				N, Female		39
PE3M0215				TNC, Male, RA		40
PE3M0212			TNC, Female	N, Male		41
PE3M0214				N, Male, RA		42
PE3M0213				N, Female		43
PE3M0211				TNC, Male, RA		44
PE3M0210				TNC, Female		45
PE-P300LL						
PE3M0240	PE-P300LL	83	TNC, Male	N, Male	18	46
PE3M0242				N, Male, RA		47
PE3M0241				N, Female		48
PE3M0238				TNC, Male		49
PE3M0239				TNC, Male, RA		50
PE3M0244			TNC, Male, RA	N, Male		51
PE3M0246				N, Male, RA		52
PE3M0245				N, Female		53
PE3M0243				TNC, Male, RA		54

Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

LOW PIM CABLE ASSEMBLIES

Product Features

- 100% PIM Tested, Results Marked on Cable
- Max Frequency 6 GHz
- Low PIM: < -160 dBc Max
- 76% Phase Velocity
- FEP Jacket
- UL910 Plenum-Rated Cable
- Lightweight and Extremely Flexible
- Low Loss with Excellent VSWR
- IP67 (when mated)
- Shielding Effectivity > 100 dB
- Connector Options: 4.3-10, SMA, QMA, 7/16 DIN, 4.1/9.5, Type-N

Applications

- Low PIM Applications
- Distributed Antenna Systems (DAS)
- Plenum Installations
- Multi-Carrier Communication Systems
- PIM Testing

Low PIM Cable Assemblies

Pasternack's Low PIM Cable Assemblies offer a wide range of connector options: 4.3-10, SMA, QMA, 7/16 DIN, 4.1/9.5, and Type-N. These assemblies deliver low PIM performance to support Distributed Antenna Systems (DAS) and other complex, multi-carrier cable installations. All low PIM assemblies are 100% PIM tested with test results marked on the cable.

Whether the need is to provide a low PIM jumper connection, low PIM test cable, or simply create a custom assembly, Pasternack has the right cable for the job. Low PIM assemblies are part of Pasternack's full line of RF components that are available for same-day shipping. We are continually adding new cables and connectors to the low PIM family. So please visit us online at www.pasternack.com to see the newest additions, or sign up for our mailing list to receive the latest news and product information.

For Custom Lengths, Metric Lengths or Special Configurations, Please call (949) 261-1920

4.1/9.5 MINI DIN LOW PIM PLENUM RATED CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
SPP-250-LLPL							
PE3C4143	SPP-250-LLPL	76	4.1/9.5 Mini DIN, Male	4.1/9.5 Mini DIN, Male	5.8	-160	1
PE3C5847				4.1/9.5 Mini DIN, Male, RA			2
PE3C5841				4.1/9.5 Mini DIN, Female			3
PE3C5834				4.3-10, Female			4
PE3C4134				7/16 DIN, Male			5
PE3C5854				7/16 DIN, Female			6
PE3W07481				N, Female			7
PE3C5866				QMA, Male		-150	8
PE3C5872				QMA, Male, RA		-145	9
PE3C5860				QMA, Female		-150	10
PE3C5885				SMA, Male		-155	11
PE3C5890				SMA, Male, RA			12
PE3C5879				SMA, Female			13
PE3C5852			4.1/9.5 Mini DIN, Male, RA	4.1/9.5 Mini DIN, Male, RA		-160	14
PE3C5846				4.3-10, Male			15
PE3C5950				4.3-10, Female			16
PE3C5848				7/16 DIN, Male			17
PE3C5849				N, Male			18
PE3C5850				QMA, Male		-150	19
PE3C5851				SMA, Male		-155	20
PE3C5840			4.1/9.5 Mini DIN, Female	4.3-10, Male		-160	21
PE3C5842				7/16 DIN, Male			22
PE3C5843				N, Male			23
PE3C5844				QMA, Male		-150	24
PE3C5845				SMA, Male		-155	25
PE-SR402FLJ Low PIM							
PE3C2009	PE-SR402FLJ Low PIM	70	4.1/9.5 Mini DIN, Male	4.1/9.5 Mini DIN, Male	3	-160	26
PE3C2010				4.1/9.5 Mini DIN, Female			27

4.3/10 DIN LOW PIM PLENUM RATED CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
SPP-250-LLPL							
PE3C4142	SPP-250-LLPL	76	4.3-10, Male	4.3-10, Male	5.8	-160	28
PE3C5833				4.3-10, Female			29
PE3C4135				7/16 DIN, Male	6		30
PE3C5853				7/16 DIN, Female	5.8		31
PE3C5865				QMA, Male		-150	32
PE3C5871				QMA, Male, RA		-145	33
PE3C5859				QMA, Female		-150	34
PE3C5884				SMA, Male		-155	35
PE3C5889				SMA, Male, RA			36
PE3C5878				SMA, Female			37
PE3C4147			4.3-10, Male, RA	4.3-10, Male	6	-160	38
PE3C4146				4.3-10, Male, RA			39
PE3C5836			4.3-10, Female	7/16 DIN, Male	5.8		40
PE3C5837				N, Male			41
PE3C5838				QMA, Male		-150	42
PE3C5839				SMA, Male		-155	43

7/16 DIN LOW PIM PLENUM RATED CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
SPP-250-LLPL							
PE3C4130	SPP-250-LLPL	76	7/16 DIN, Male	7/16 DIN, Male	6	-160	44
PE3C5855				7/16 DIN, Female	5.8		45
PE3C5867				QMA, Male		-150	46
PE3C5873				QMA, Male, RA		-145	47
PE3C5861				QMA, Female		-150	48
PE3C5886				SMA, Male		-155	49
PE3C5891				SMA, Male, RA			50
PE3C5880				SMA, Female			51
PE3C4131			7/16 DIN, Male, RA	7/16 DIN, Male	6	-160	52
SPP-250-LLPL							
PE3C4144	SPP-250-LLPL	76	7/16 DIN, Male, RA	7/16 DIN, Male, RA	6	-160	53
PE3C5856			7/16 DIN, Female	N, Male	5.8		54
PE3C5857				QMA, Male		-150	55
PE3C5858				SMA, Male		-155	56
PE-SR402FLJ Low PIM							
PE3C2003	PE-SR402FLJ Low PIM	70	7/16 DIN, Male	7/16 DIN, Male	3	-160	57
PE3C2004				7/16 DIN, Female			58
PE-SR401FLJ Low PIM							
PE3C2013	PE-SR401FLJ Low PIM	70	7/16 DIN, Male	7/16 DIN, Male	3	-160	59
PE3C2015				7/16 DIN, Female			60

QMA LOW PIM PLENUM RATED CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
SPP-250-LLPL							
PE3C5869	SPP-250-LLPL	76	QMA, Male	QMA, Male	5.8	-150	61
PE3C5875				QMA, Male, RA		-145	62
PE3C5863				QMA, Female		-150	63
PE3C5870				SMA, Male			64
PE3C5893				SMA, Male, RA			65
PE3C5882				SMA, Female			66
PE3C5877			QMA, Male, RA	QMA, Male, RA		-145	67
PE3C5876				SMA, Male			68
PE3C5864			QMA, Female			-150	69

SMA LOW PIM PLENUM RATED CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
SPP-250-LLPL							
PE3C5888	SPP-250-LLPL	76	SMA, Male	SMA, Male	5.8	-155	70
PE3C5894				SMA, Male, RA			71
PE3C5883				SMA, Female			72
PE3C5895			SMA, Male, RA	SMA, Male, RA			73
PE-SR402FLJ Low PIM							
PE3C2007	PE-SR402FLJ Low PIM	70	SMA, Male	7/16 DIN, Male	3	-150	74
PE3C2008				SMA, Male	6		75

TYPE N LOW PIM PLENUM RATED CABLE ASSEMBLY SERIES

Model No	Cable Type	Velocity of Propagation (%)	Connector 1	Connector 2	Freq. Max. (GHz)	PIM (dBc)	ROW
SPP-250-LLPL							
PE3C4140	SPP-250-LLPL	76	N, Male	4.1/9.5 Mini DIN, Male	6	-160	76
PE3C4141				4.3-10, Male			77
PE3C4132				7/16 DIN, Male			78
PE3C4136				7/16 DIN, Male, RA			79
PE3C4137				N, Male			80
PE3C5868				QMA, Male	5.8	-150	81
PE3C5874				QMA, Male, RA		-145	82
PE3C5862				QMA, Female		-150	83
PE3C5887				SMA, Male		-155	84
PE3C5892				SMA, Male, RA			85
PE3C5881				SMA, Female		-160	86
PE3C4139			N, Male, RA	N, Male	6		87
PE3C4145				N, Male, RA	5.8		88
PE3C4133			N, Female	7/16 DIN, Male	6		89
PE3C4138				N, Male	5.8		90
PE3W07489				N, Female			91
PE-SR402FLJ Low PIM							
PE3C2002	PE-SR402FLJ Low PIM	70	N, Male	7/16 DIN, Male	3	-160	92
PE3C2005				7/16 DIN, Female			93
PE3C2000				N, Male	6		94
PE3C2001				N, Female			95
PE3C2006				SMA, Male		-150	96
PE-SR401FLJ Low PIM							
PE3C2012	PE-SR401FLJ Low PIM	70	N, Male	7/16 DIN, Male	3	-160	97
PE3C2014				7/16 DIN, Female			98
PE3C2011				N, Male			99

Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

1.0/2.3 PLUG TO BNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W05192				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$41.75	$42.57	$43.38	$44.17	$44.98	$42.28	See Web

1

1.0/2.3 PLUG RIGHT ANGLE TO BNC MALE

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C3469				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$50.54	$51.04	$54.41	$57.23	$60.58	$49.83	See Web

2

1.0/2.3 JACK BULKHEAD TO 1.0/2.3 JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C0441				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$52.79	$55.47	$58.67	$61.88	$65.06	$68.24	See Web

3

1.0MM MALE TO 1.0MM MALE

Precision Flexible Cable Assemblies

PE-110TC Coax, 50 Ohm

Part No. PE3TC1220				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						
6"	12"	24"	100CM	-	-	Custom Len.
$6,373.75	$8,529.33	Call	Call	-	-	See Web

4

1.0MM MALE TO 1.0MM FEMALE

Precision Flexible Cable Assemblies

PE-110TC Coax, 50 Ohm

Part No. PE3TC1221				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						
10CM	13CM	6"	12"	18"	-	Custom Len.
Call	Call	$6,373.75	$6,652.90	Call	-	See Web

5

1.85MM MALE TO 1.85MM MALE

Low Loss Flexible Cable Assemblies

PE-P106LL Coax, 50 Ohm

Part No. PE3C5998				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.106" dia.		
6"	12"	24"	36"	50CM	100CM	Custom Len.
$617.74	$641.49	$640.87	$704.81	$619.87	$726.11	See Web

6

Low Loss Semi-Rigid Cable Assemblies

PECX001 Coax, 50 Ohm

Part No. PE3C6484				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					30 dB/100ft	101 W
6"	12"	18"	24"	36"	48"	Custom Len.
$288.18	$288.18	$288.72	$289.23	$290.27	$291.33	See Web

PECX002 Coax, 50 Ohm

Part No. PE3C6487				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					30 dB/100ft	101 W
6"	12"	18"	24"	36"	48"	Custom Len.
$292.39	$292.39	$293.10	$293.80	$295.20	$296.60	See Web

7, 8

PECX003 Coax, 50 Ohm

Part No. PE3C6490				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					20 dB/100ft	188 W
6"	12"	18"	24"	36"	48"	Custom Len.
$295.62	$295.62	$296.47	$297.30	$298.97	$300.64	See Web

PECX004 Coax, 50 Ohm

Part No. PE3C6491				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					20 dB/100ft	188 W
6"	12"	18"	24"	36"	48"	Custom Len.
$298.13	$298.13	$299.08	$300.03	$301.90	$303.79	See Web

9, 10

Precision Flexible Cable Assemblies

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC0800				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.27" dia.		
30CM	60CM	24"	36"	48"	241"	Custom Len.
Call	Call	$3,127.53	$3,168.72	$3,279.23	Call	See Web

11

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE36521				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W
6"	12"	18"	24"	36"	48"	Custom Len.
$410.49	$410.49	$414.49	$418.49	$426.48	$434.46	See Web

12

PE-SR405FL Coax, 50 Ohm

Part No. PE36525				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W
6"	12"	18"	24"	36"	48"	Custom Len.
$364.34	$364.34	$370.16	$375.96	$387.55	$399.15	See Web

13

Standard Flexible Cable Assemblies

PE-P086 Coax, 50 Ohm

Part No. PE3C0752				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	23 dB/100ft	160 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$244.42	$253.03	$261.64	$270.74	$254.32	$234.38	See Web

14

PE-P103 Coax, 50 Ohm

Part No. PE3C6638				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.103" dia.	29.48 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$277.16	$305.35	$333.58	$361.79	$390.02	$295.20	See Web

15

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE36519				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W
6"	12"	18"	24"	36"	48"	Custom Len.
$432.66	$413.66	$419.20	$450.48	$435.86	$446.96	See Web

16

RG405/U Coax, 50 Ohm

Part No. PE36523				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W
6"	12"	18"	24"	36"	48"	Custom Len.
$360.08	$360.08	$363.80	$367.53	$374.97	$382.41	See Web

17

Skew Matched Pair Flexible Cable Assemblies

PE-P106LL Coax, 50 Ohm

Part No. PE3C5835				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.106" dia.		
12"	24"	36"	48"	-	-	Custom Len.
$3,383.88	$3,606.16	$4,339.86	$4,559.14	-	-	See Web

18

1.85MM MALE TO 1.85MM MALE RIGHT ANGLE

Precision Flexible Cable Assemblies

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC1000				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.27" dia.		
24"	36"	48"	-	-	-	Custom Len.
$3,637.51	Call	$3,792.44	-	-	-	See Web

19

1.85MM MALE TO 1.85MM FEMALE

Precision Flexible Cable Assemblies

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC0900				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.27" dia.		
24"	36"	48"	-	-	-	Custom Len.
$3,127.53	$3,168.72	$3,279.23	-	-	-	See Web

20

1.85MM MALE TO 2.4MM MALE

Standard Flexible Cable Assemblies

PE-P103 Coax, 50 Ohm

Part No. PE3C6639				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.103" dia.	29.48 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$281.11	$308.42	$335.70	$363.00	$390.28	$298.59	See Web

21

1.85MM MALE TO 2.92MM MALE

Low Loss Semi-Rigid Cable Assemblies

Continued on Next Page

See Our Website For Current Pricing & Real-Time Stock Availability!

PECX001 Coax, 50 Ohm

Part No. PE3C6485				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					30 dB/100ft	101 W	22
6"	12"	18"	24"	36"	48"	Custom Len.	
$279.80	$279.80	$280.33	$280.85	$281.89	$282.94	See Web	

PECX002 Coax, 50 Ohm

Part No. PE3C6488				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					30 dB/100ft	101 W	23
6"	12"	18"	24"	36"	48"	Custom Len.	
$284.01	$284.01	$284.72	$285.41	$286.82	$288.22	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W07895				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	24
12"	18"	24"	36"	48"	60"	Custom Len.	
$277.39	$271.67	$276.33	$285.68	$295.02	$304.37	See Web	

1.85MM FEMALE TO 1.85MM FEMALE

Precision Flexible Cable Assemblies

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC0950				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.27" dia.			25
24"	48"	-	-	-	-	Custom Len.	
$3,295.73	$3,444.42	-	-	-	-	See Web	

2.2-5 MALE TO 4.3-10 MALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C8050				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		26
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.08	$75.75	$79.41	$83.07	$86.73	$70.77	See Web	

2.2-5 MALE TO 4.3-10 MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C8051				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		27
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.24	$77.91	$81.57	$85.23	$88.89	$72.93	See Web	

2.2-5 MALE TO 4.3-10 FEMALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C8052				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		28
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.16	$76.83	$80.49	$84.15	$87.81	$71.85	See Web	

2.2-5 MALE TO 4.3-10 FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C8053				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		29
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.24	$77.91	$81.57	$85.23	$88.89	$72.93	See Web	

2.2-5 MALE TO 4.3-10 FEMALE 4 HOLE FLANGE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C8054				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		30
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.32	$78.99	$82.65	$86.31	$89.97	$74.01	See Web	

2.2-5 MALE TO N MALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C8059				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		31
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.68	$70.35	$74.01	$77.67	$81.33	$65.37	See Web	

2.2-5 MALE TO N MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C8060				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		32
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.38	$73.05	$76.71	$80.37	$84.03	$68.07	See Web	

2.2-5 MALE TO N FEMALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C8061				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		33
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.68	$70.35	$74.01	$77.67	$81.33	$65.37	See Web	

2.2-5 MALE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C8062				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		34
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.68	$70.35	$74.01	$77.67	$81.33	$65.37	See Web	

2.2-5 MALE TO 2.2-5 MALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7856				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		35
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.11	$72.84	$76.57	$80.29	$84.02	$71.50	See Web	

2.2-5 MALE TO 2.2-5 MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7857				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		36
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.70	$79.44	$83.16	$86.89	$90.62	$78.09	See Web	

2.2-5 MALE TO 2.2-5 FEMALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7858				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		37
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.11	$72.84	$76.57	$80.29	$84.02	$71.50	See Web	

2.2-5 MALE TO 2.2-5 FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7859				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		38
12"	24"	36"	48"	60"	50CM	Custom Len.	
$71.86	$75.58	$79.31	$83.04	$86.77	$74.24	See Web	

2.2-5 MALE RIGHT ANGLE TO 2.2-5 MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7860				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	39
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$82.30	$86.03	$89.75	$93.49	$97.22	$84.69	See Web	

2.2-5 MALE RIGHT ANGLE TO 2.2-5 FEMALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7861				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	40
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.70	$79.44	$83.16	$86.89	$90.62	$78.09	See Web	

2.2-5 MALE RIGHT ANGLE TO 2.2-5 FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7862				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	41
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$78.46	$82.18	$85.91	$89.63	$93.36	$80.84	See Web	

2.2-5 FEMALE TO 4.3-10 MALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C8055				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	42
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.08	$75.75	$79.41	$83.07	$86.73	$70.77	See Web	

2.2-5 FEMALE TO 4.3-10 MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C8056				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	43
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.24	$77.91	$81.57	$85.23	$88.89	$72.93	See Web	

2.2-5 FEMALE TO 4.3-10 FEMALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C8057				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	44
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.16	$76.83	$80.49	$84.15	$87.81	$71.85	See Web	

2.2-5 FEMALE TO 4.3-10 FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C8058				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	45
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.24	$77.91	$81.57	$85.23	$88.89	$72.93	See Web	

2.2-5 FEMALE TO N MALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C8063				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	46
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.68	$70.35	$74.01	$77.67	$81.33	$65.37	See Web	

2.2-5 FEMALE TO N MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C8064				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	47
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.38	$73.05	$76.71	$80.37	$84.03	$68.07	See Web	

2.2-5 FEMALE TO N FEMALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C8065				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	48
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.68	$70.35	$74.01	$77.67	$81.33	$65.37	See Web	

2.2-5 FEMALE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C8066				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	49
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.68	$70.35	$74.01	$77.67	$81.33	$65.37	See Web	

2.4MM MALE TO 1.85MM MALE

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W08014				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	50
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	
12"	18"	24"	36"	48"	60"	Custom Len.	
$285.72	$279.68	$284.36	$293.70	$303.05	$312.39	See Web	

2.4MM MALE TO 2.4MM MALE

Flexible Flexible Cable Assemblies

PE-P086HF Coax, 50 Ohm

Part No. PE3C7803				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	51
1 piece price shown. See web or call for volume pricing.				0.104" dia.	21.1 dB/100ft		
12"	18"	24"	36"	48"	60"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

Precision Flexible Cable Assemblies

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC0500				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	52
1 piece price shown. See web or call for volume pricing.				0.27" dia.			
24"	36"	48"	-	-	-	Custom Len.	
$3,024.23	Call	$3,179.00	-	-	-	See Web	

Test Flexible Cable Assemblies

PE-P160 Coax, 50 Ohm

Part No. PE363				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	53
1 piece price shown. See web or call for volume pricing.				0.16" dia.	12.62 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
Call	Call	$367.89	$395.96	Call	Call	See Web	

Standard Flexible Cable Assemblies

PE-P086HF Coax, 50 Ohm

Part No. PE3C5984				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	54
1 piece price shown. See web or call for volume pricing.				0.104" dia.	21.1 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$219.66	$227.87	$236.08	$244.29	$252.51	$216.71	See Web	

PE-P103 Coax, 50 Ohm

Part No. PE3C6640				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	55
1 piece price shown. See web or call for volume pricing.				0.103" dia.	29.48 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$292.03	$320.14	$331.72	$359.84	$406.68	$293.53	See Web	

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA4004				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	56
1 piece price shown. See web or call for volume pricing.				0.43" dia.			
24"	48"	700CM	-	-	-	Custom Len.	
$2,138.38	$2,358.66	Call	-	-	-	See Web	

2.4MM MALE TO 2.4MM MALE RIGHT ANGLE

Precision Flexible Cable Assemblies

Continued on Next Page

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC0700				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.27" dia.		
24"	36"	48"	-	-	-	Custom Len.
$3,537.13	Call	$3,688.49	-	-	-	See Web

57

2.4MM MALE TO 2.4MM FEMALE

Flexible Cable Assemblies

PE-P160 Coax, 50 Ohm

Part No. PE364				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.155" dia.	12.62 dB/100ft	1,070 W
12"	24"	36"	48"	60"	50CM	Custom Len.
Call	Call	$380.88	$403.45	Call	Call	See Web

58

Precision Flexible Cable Assemblies

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC0600				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.27" dia.		
24"	36"	48"	120"	-	-	Custom Len.
$3,024.23	Call	$3,179.00	Call	-	-	See Web

59

Standard Flexible Cable Assemblies

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA4005				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.43" dia.		
24"	48"	-	-	-	-	Custom Len.
$2,292.19	$2,521.07	-	-	-	-	See Web

60

2.4MM FEMALE TO 2.4MM FEMALE

Precision Flexible Cable Assemblies

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC0650				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.27" dia.		
24"	48"	70CM	-	-	-	Custom Len.
$3,193.51	$3,345.30	Call	-	-	-	See Web

61

2.4MM FEMALE BULKHEAD TO SMA MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE3W03550				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$189.20	$201.87	$214.53	$227.19	$239.84	$197.31	See Web

62

2.92MM MALE TO 1.85MM MALE

Standard Flexible Cable Assemblies

PE-P103 Coax, 50 Ohm

Part No. PE3C6636				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.103" dia.	29.48 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$253.53	$280.82	$308.12	$335.41	$362.71	$270.99	See Web

63

2.92MM MALE TO 2.4MM MALE

Standard Flexible Cable Assemblies

PE-P103 Coax, 50 Ohm

Part No. PE3C6637				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.103" dia.	29.48 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$231.05	$258.33	$285.64	$312.92	$340.22	$248.51	See Web

64

2.92MM MALE TO 2.92MM MALE

Skew Matched Pair Flexible Cable Assemblies

PE-125LLS Coax, 50 Ohm

Part No. PE3C4680				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.124" dia.		
12"	24"	36"	48"	-	-	Custom Len.
$1,173.34	$1,300.04	Call	$1,553.43	-	-	See Web

65

Flexible Cable Assemblies

PE-P160 Coax, 50 Ohm

Part No. PE360					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.155" dia.	12.62 dB/100ft	1,070 W
12"	24"	36"	48"	60"	72"	Custom Len.	
$248.20	$271.61	$295.04	$318.47	$341.89	$362.97	See Web	

66

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C0835					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						22 dB/100ft	130 W
6"	12"	18"	24"	36"	48"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

67

Low Loss Semi-Rigid Cable Assemblies

PECX001 Coax, 50 Ohm

Part No. PE3C6486					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						30 dB/100ft	101 W
6"	12"	18"	24"	36"	48"	Custom Len.	
$271.42	$271.42	$271.94	$272.46	$273.52	$274.56	See Web	

68

PECX002 Coax, 50 Ohm

Part No. PE3C6489					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						30 dB/100ft	101 W
6"	12"	18"	24"	36"	48"	Custom Len.	
$275.63	$275.63	$276.34	$277.03	$278.44	$279.83	See Web	

69

PECX005 Coax, 50 Ohm

Part No. PE3C6492					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						17 dB/100ft	314 W
6"	12"	18"	24"	36"	48"	Custom Len.	
$268.01	$268.01	$268.40	$268.79	$269.55	$270.31	See Web	

70

PECX006 Coax, 50 Ohm

Part No. PE3C6493					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						17 dB/100ft	231 W
6"	12"	18"	24"	36"	48"	Custom Len.	
$270.54	$270.54	$271.02	$271.51	$272.47	$273.45	See Web	

71

Test Flexible Cable Assemblies

PE-VNA Coax, 50 Ohm

Part No. PE319					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.							
8"	20"	24"	36"	40"	48"	Custom Len.	
Call	Call	$1,237.79	$1,384.26	Call	$1,425.42	See Web	

72

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE34733					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						11.88 dB/100ft	450 W
6"	12"	18"	24"	36"	48"	Custom Len.	
$142.09	$146.34	$150.72	$146.23	$163.87	$162.58	See Web	

73

PE-SR405FL Coax, 50 Ohm

Part No. PE3C1377					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						22.5 dB/100ft	130 W
6"	12"	18"	24"	36"	48"	Custom Len.	
$181.97	$181.97	$187.75	$193.55	$205.13	$216.73	See Web	

74

Standard Flexible Cable Assemblies

PE-P086 Coax, 50 Ohm

Part No. PE3C0666					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.104" dia.	23 dB/100ft	160 W
6"	12"	18"	24"	36"	48"	Custom Len.	
$175.61	$179.79	$184.09	$188.39	$197.01	$206.13	See Web	

75

PE-P103 Coax, 50 Ohm

Part No. PE3C6635					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.103" dia.	29.48 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$272.67	$300.78	$318.39	$346.50	$387.31	$280.19	See Web	

76

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA2605					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.43" dia.		
24"	48"	-	-	-	-	Custom Len.	
$1,616.99	$1,826.81	-	-	-	-	See Web	

77

Part No. PE3VNA4001					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.43" dia.		
-	24"	36"	48"	60"	96"	Custom Len.	
-	$2,087.53	$2,142.98	$2,307.83	$2,432.44	Call	See Web	

78

Standard Semi-Rigid Cable Assemblies

PE-118SR Coax, 50 Ohm

Part No. PE3W07491					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.						12.5 dB/100ft	500 W
6"	12"	18"	24"	36"	48"	Custom Len.	
$310.52	$310.52	$312.47	$314.41	$318.31	$322.21	See Web	

79

PE-SR402AL Coax, 50 Ohm

Part No. PE34731					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					0.141" dia.	13 dB/100ft	450 W
6"	12"	18"	24"	36"	48"	Custom Len.	
$143.23	$140.17	$145.28	$159.62	$160.59	$170.79	See Web	

80

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

RG402/U Coax, 50 Ohm

Part No. PE34729				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	81
6"	12"	18"	24"	36"	48"	Custom Len.	
$142.00	$146.11	$150.36	$154.59	$163.08	$161.60	See Web	

2.92MM MALE TO 2.92MM FEMALE

Test Flexible Cable Assemblies

PE-P160 Coax, 50 Ohm

Part No. PE361				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.	12.62 dB/100ft		82
12"	24"	36"	48"	60"	50CM	Custom Len.	
$290.42	$318.49	$346.57	$374.63	$402.70	$308.42	See Web	

Standard Flexible Cable Assemblies

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA2606				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			83
24"	48"	-	-	-	-	Custom Len.	
$1,649.29	$1,745.63	-	-	-	-	See Web	
Part No. PE3VNA4002				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			84
24"	48"	85"	-	-	-	Custom Len.	
$2,155.32	$2,375.62	Call	-	-	-	See Web	

2.92MM MALE TO 2.92MM FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE34745				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	85
6"	12"	18"	24"	36"	48"	Custom Len.	
$219.78	$219.78	$223.86	$227.96	$236.13	$244.31	See Web	

Standard Semi-Rigid Cable Assemblies

PE-SR402AL Coax, 50 Ohm

Part No. PE34743				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	86
6"	12"	18"	24"	36"	48"	Custom Len.	
$238.67	$221.84	$249.55	$255.06	$242.26	$252.46	See Web	

3.5MM MALE TO 1.85MM MALE

Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE36537				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	87
6"	12"	18"	24"	36"	48"	Custom Len.	
$285.69	$291.28	$296.94	$302.53	$313.78	$325.05	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE36535				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	88
6"	12"	18"	24"	36"	48"	Custom Len.	
$283.66	$287.24	$290.89	$294.45	$301.68	$308.90	See Web	

3.5MM MALE TO 3.5MM MALE

Test Flexible Cable Assemblies

PE-P160 Coax, 50 Ohm

Part No. PE369				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.	12.62 dB/100ft		89
12"	24"	36"	48"	60"	50CM	Custom Len.	
Call	Call	$333.95	$362.03	$390.10	Call	See Web	

PE-VNA Coax, 50 Ohm

Part No. PE315				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.							90
24"	36"	48"	60"	72"	-	Custom Len.	
$1,095.24	$1,311.93	$1,306.77	$1,519.88	$1,654.94	-	See Web	

Standard Flexible Cable Assemblies

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA2603				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			91
24"	36"	48"	60"	-	-	Custom Len.	
$1,584.74	$1,854.96	$1,794.54	$2,083.76	-	-	See Web	

Standard Semi-Rigid Cable Assemblies

PE-SR402AL Coax, 50 Ohm

Part No. PE34572				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	92
6"	12"	18"	24"	36"	48"	Custom Len.	
$242.53	$247.88	$253.39	$258.91	$269.96	$264.48	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34576				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	93
6"	12"	18"	24"	36"	48"	Custom Len.	
$244.01	$244.01	$248.67	$253.36	$262.75	$272.10	See Web	

RG402/U Coax, 50 Ohm

Part No. PE34570				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	94
6"	12"	18"	24"	36"	48"	Custom Len.	
$231.53	$231.53	$235.47	$239.44	$247.35	$255.27	See Web	

RG405/U Coax, 50 Ohm

Part No. PE34574				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	95
6"	12"	18"	24"	36"	48"	Custom Len.	
$242.07	$242.07	$245.80	$249.51	$256.97	$281.22	See Web	

3.5MM MALE TO 3.5MM FEMALE

Test Flexible Cable Assemblies

PE-VNA Coax, 50 Ohm

Part No. PE317				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.							96
24"	36"	48"	60"	72"	-	Custom Len.	
$1,104.91	$1,181.86	$1,420.85	$1,381.59	$1,549.31	-	See Web	

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE35121				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	97
12"	24"	36"	48"	60"	-	Custom Len.	
$251.54	$245.47	$253.63	$261.80	$269.98	-	See Web	
Part No. PE3W03922				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	400 W	98
12"	24"	36"	48"	60"	50CM	Custom Len.	
$207.13	$215.65	$224.14	$232.64	$241.15	$212.58	See Web	

Standard Flexible Cable Assemblies

PE-FF430 Coax, 50 Ohm

Part No. PE3C4012				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			99
100CM	-	-	-	-	-	Custom Len.	
$945.57	-	-	-	-	-	See Web	

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA2604				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			1
24"	36"	48"	60"	-	-	Custom Len.	
$1,616.99	$1,890.17	$1,826.81	$2,118.97	-	-	See Web	

Standard Semi-Rigid Cable Assemblies

PE-SR402AL Coax, 50 Ohm

Part No. PE34580				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	2
6"	12"	18"	24"	36"	48"	Custom Len.	
$239.39	$239.39	$244.47	$249.59	$259.78	$287.49	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34584				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	3
6"	12"	18"	24"	36"	48"	Custom Len.	
Call	$298.94	Call	$308.00	$317.10	$326.16	See Web	

RG402/U Coax, 50 Ohm

Part No. PE34578				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	4
6"	12"	18"	24"	36"	48"	Custom Len.	
$247.15	$237.04	$241.00	$244.95	$252.87	$260.79	See Web	

RG405/U Coax, 50 Ohm

Part No. PE34582				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	5
6"	12"	18"	24"	36"	48"	Custom Len.	
$314.88	$314.88	$318.61	$322.34	$329.78	$358.41	See Web	

3.5MM MALE TO 3.5MM FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Semi-Rigid Cable Assemblies

PE-SR402AL Coax, 50 Ohm

Part No. PE34588				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	6
6"	12"	18"	24"	36"	48"	Custom Len.	
$422.33	$427.27	$432.21	$437.14	$447.06	$456.93	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-SR405AL Coax, 50 Ohm

Part No. PE34592				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	7
6"	12"	18"	24"	36"	48"	Custom Len.	
$253.21	$257.70	$262.26	$266.81	$275.86	$284.98	See Web	

RG402/U Coax, 50 Ohm

Part No. PE34586				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	8
6"	12"	18"	24"	36"	48"	Custom Len.	
$421.21	$425.06	$428.90	$432.73	$440.41	$448.08	See Web	

RG405/U Coax, 50 Ohm

Part No. PE34590				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	9
6"	12"	18"	24"	36"	48"	Custom Len.	
$252.23	$255.88	$259.45	$263.10	$270.27	$277.49	See Web	

3.5MM FEMALE TO 3.5MM FEMALE

Standard Flexible Cable Assemblies

PE-FF430 Coax, 50 Ohm

Part No. PE3C4013				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			10
100CM	-	-	-	-	-	Custom Len.	
$945.57	-	-	-	-	-	See Web	

4.1/9.5 MINI DIN MALE TO 4.1/9.5 MINI DIN MALE

Low PIM Formable Cable Assemblies

PE-SR402FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2009				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.			11
50CM	100CM	200CM	-	-	-	Custom Len.	
Call	$112.41	$134.57	-	-	-	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7819				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		12
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.71	$68.44	$72.17	$75.90	$79.62	$67.09	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4143				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	13
"	12"	24"	36"	48"	60"	Custom Len.	
Call	$101.58	$107.71	$112.27	$118.32	$124.37	See Web	

4.1/9.5 MINI DIN MALE TO 4.1/9.5 MINI DIN MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7820				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		14
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.66	$73.39	$77.12	$80.84	$84.57	$72.04	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5847				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			15
12"	24"	36"	48"	60"	50CM	Custom Len.	
$106.74	$111.31	$117.36	$123.41	$129.46	$109.15	See Web	

4.1/9.5 MINI DIN MALE TO 4.1/9.5 MINI DIN FEMALE

Low PIM Formable Cable Assemblies

PE-SR402FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2010				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.			16
100CM	200CM	-	-	-	-	Custom Len.	
$137.98	Call	-	-	-	-	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7821				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		17
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.56	$72.29	$76.02	$79.74	$83.47	$70.95	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5841				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			18
12"	24"	36"	48"	60"	50CM	Custom Len.	
$98.79	$104.93	$109.52	$115.57	$121.62	$102.73	See Web	

4.1/9.5 MINI DIN MALE TO 4.1/9.5 MINI DIN FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7822				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		19
12"	24"	36"	48"	60"	50CM	Custom Len.	
$71.31	$75.03	$78.76	$82.50	$86.22	$73.69	See Web	

4.1/9.5 MINI DIN MALE TO 4.3-10 FEMALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5834				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			20
12"	24"	36"	48"	60"	50CM	Custom Len.	
$98.79	$104.93	$109.52	$115.57	$121.62	$102.73	See Web	

4.1/9.5 MINI DIN MALE TO 7/16 DIN MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4134				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			21
12"	24"	36"	48"	60"	50CM	Custom Len.	
$112.97	$108.74	$114.79	$120.84	$126.89	$106.57	See Web	

4.1/9.5 MINI DIN MALE TO 7/16 DIN FEMALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5854				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			22
12"	24"	36"	48"	60"	50CM	Custom Len.	
$98.79	$104.93	$109.52	$115.57	$121.62	$102.73	See Web	

4.1/9.5 MINI DIN MALE TO N FEMALE

Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3W07481				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			23
12"	24"	36"	48"	60"	50CM	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

4.1/9.5 MINI DIN MALE TO QMA MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5866				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			24
12"	24"	36"	48"	60"	50CM	Custom Len.	
$86.90	$93.04	$99.17	$105.29	$109.88	$90.82	See Web	

4.1/9.5 MINI DIN MALE TO QMA MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5872				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			25
12"	24"	36"	48"	60"	50CM	Custom Len.	
$89.29	$95.42	$101.56	$107.69	$112.25	$93.21	See Web	

4.1/9.5 MINI DIN MALE TO QMA FEMALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5860				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			26
12"	24"	36"	48"	60"	50CM	Custom Len.	
$82.94	$89.07	$95.21	$101.34	$107.48	$86.88	See Web	

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

See Our Website For Current Pricing & Real-Time Stock Availability!

4.1/9.5 MINI DIN MALE TO SMA MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5885				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			27
12"	24"	36"	48"	60"	50CM	Custom Len.	
$78.96	$85.09	$91.22	$97.36	$103.49	$82.88	See Web	

4.1/9.5 MINI DIN MALE TO SMA MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5890				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			28
12"	24"	36"	48"	60"	50CM	Custom Len.	
$80.55	$86.69	$92.82	$98.95	$105.10	$84.48	See Web	

4.1/9.5 MINI DIN MALE TO SMA FEMALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5879				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			29
12"	24"	36"	48"	60"	50CM	Custom Len.	
$79.75	$85.89	$92.02	$98.16	$104.29	$83.68	See Web	

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO 4.1/9.5 MINI DIN MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7823				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		30
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.61	$78.34	$82.06	$85.79	$89.52	$77.00	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5852				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			31
12"	24"	36"	48"	60"	50CM	Custom Len.	
$117.01	$123.06	$129.10	$135.15	$141.20	$120.87	See Web	
Part No. PE3C6172				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	32
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.37	$79.50	$85.64	$91.77	$97.91	$77.29	See Web	

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO 4.1/9.5 MINI DIN FEMALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7824				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		33
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.51	$77.24	$80.96	$84.69	$88.41	$75.90	See Web	

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO 4.1/9.5 MINI DIN FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7825				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		34
12"	24"	36"	48"	60"	50CM	Custom Len.	
$76.25	$79.98	$83.72	$87.44	$91.17	$78.64	See Web	

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO 4.3-10 MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5846				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			35
12"	24"	36"	48"	60"	50CM	Custom Len.	
$106.74	$111.31	$117.36	$123.41	$129.46	$109.15	See Web	

Part No. PE3C6173				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	36
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.05	$78.19	$84.33	$90.47	$96.60	$75.97	See Web	

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO 4.3-10 FEMALE

Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5950				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			37
12"	24"	36"	48"	60"	50CM	Custom Len.	
$109.17	$115.22	$121.27	$127.32	$133.36	$113.02	See Web	

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO 7/16 DIN MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5848				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			38
12"	24"	36"	48"	60"	50CM	Custom Len.	
$109.17	$115.22	$121.27	$127.32	$133.36	$113.03	See Web	
Part No. PE3C6187				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	39
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.12	$74.24	$80.38	$86.51	$92.65	$72.03	See Web	

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO N MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5849				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			40
12"	24"	36"	48"	60"	50CM	Custom Len.	
$102.77	$107.39	$113.44	$119.49	$125.54	$106.69	See Web	
Part No. PE3C6218				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	41
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.50	$71.62	$77.75	$83.89	$90.02	$69.41	See Web	

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO N MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6234				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	42
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.12	$74.24	$80.38	$86.51	$92.65	$72.03	See Web	

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO QMA MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5850				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			43
12"	24"	36"	48"	60"	50CM	Custom Len.	
$98.79	$104.93	$109.52	$115.57	$121.62	$102.73	See Web	

4.1/9.5 MINI DIN MALE RIGHT ANGLE TO SMA MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5851				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			44
12"	24"	36"	48"	60"	50CM	Custom Len.	
$90.85	$96.99	$103.12	$107.74	$113.79	$94.80	See Web	

4.1/9.5 MINI DIN FEMALE TO 4.3-10 MALE

Low PIM Corrugated Cable Assemblies

Continued on Next Page

See Our Website For Current Pricing & Real-Time Stock Availability!

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5840				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	45
1 piece price shown. See web or call for volume pricing.				0.28" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$98.79	$104.93	$109.52	$115.57	$121.62	$102.73	See Web	

4.1/9.5 MINI DIN FEMALE TO 7/16 DIN MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5842				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	46
1 piece price shown. See web or call for volume pricing.				0.28" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$102.76	$107.38	$113.43	$119.48	$125.53	$106.68	See Web	

4.1/9.5 MINI DIN FEMALE TO N MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5843				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	47
1 piece price shown. See web or call for volume pricing.				0.28" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$94.82	$100.95	$107.09	$111.64	$117.69	$98.74	See Web	

4.1/9.5 MINI DIN FEMALE TO QMA MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5844				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	48
1 piece price shown. See web or call for volume pricing.				0.28" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$90.84	$96.98	$103.11	$107.73	$113.78	$94.79	See Web	

4.1/9.5 MINI DIN FEMALE TO SMA MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5845				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	49
1 piece price shown. See web or call for volume pricing.				0.28" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$82.91	$89.04	$95.17	$101.31	$107.44	$86.84	See Web	

4.3-10 MALE TO 4.3-10 MALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7826				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	50
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.20	$73.94	$77.67	$81.39	$85.12	$72.59	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4142				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	51
1 piece price shown. See web or call for volume pricing.				0.28" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$101.58	$107.71	$112.27	$118.32	$124.37	$105.50	See Web	
Part No. PE3C6175				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	52
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.73	$76.87	$83.00	$89.14	$95.27	$74.67	See Web	
Part No. PE3C6178				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	53
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.73	$76.87	$83.00	$89.14	$95.27	$74.67	See Web	
Part No. PE3C6179				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	54
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.73	$76.87	$83.00	$89.14	$95.27	$74.67	See Web	

SPP-500-LLPL Coax, 50 Ohm

Part No. PE3C6363				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	55
1 piece price shown. See web or call for volume pricing.				0.5" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.82	$75.09	$85.37	$95.66	$105.94	$71.39	See Web	

SPP-375-LLPL Coax, 50 Ohm

Part No. PE3C6380				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	56
1 piece price shown. See web or call for volume pricing.				0.402" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.15	$73.14	$81.13	$89.13	$97.14	$70.28	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C6437				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	57
1 piece price shown. See web or call for volume pricing.				0.303" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.73	$73.02	$75.31	$77.60	$79.88	$72.20	See Web	

SPF-375 Coax, 50 Ohm

Part No. PE3C6445				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	58
1 piece price shown. See web or call for volume pricing.				0.435" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$76.86	$81.10	$85.34	$89.58	$93.81	$79.59	See Web	

SPO-375 Coax, 50 Ohm

Part No. PE3C6498				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	59
1 piece price shown. See web or call for volume pricing.				0.43" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$76.86	$80.01	$83.18	$86.33	$89.47	$78.89	See Web	

SPO-500 Coax, 50 Ohm

Part No. PE3C6513				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	60
1 piece price shown. See web or call for volume pricing.				0.53" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$57.62	$60.70	$63.79	$66.87	$69.96	$59.59	See Web	

SPF-500 Coax, 50 Ohm

Part No. PE3C6516				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	61
1 piece price shown. See web or call for volume pricing.				0.545" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.92	$63.30	$67.69	$72.07	$76.47	$61.74	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C6605				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	62
1 piece price shown. See web or call for volume pricing.				0.303" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.73	$73.02	$75.31	$77.60	$79.88	$72.20	See Web	

4.3-10 MALE TO 4.3-10 MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7827				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	63
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.41	$76.13	$79.86	$83.59	$87.31	$74.79	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6176				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	64
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.05	$78.19	$84.33	$90.47	$96.60	$75.97	See Web	
Part No. PE3C6180				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	65
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.05	$78.19	$84.33	$90.47	$96.60	$75.97	See Web	

4.3-10 MALE TO 4.3-10 FEMALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7828				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	66
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$71.31	$75.03	$78.76	$82.50	$86.22	$73.69	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5833				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	67
1 piece price shown. See web or call for volume pricing.				0.28" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$98.79	$104.93	$109.52	$115.57	$121.62	$102.73	See Web	
Part No. PE3C6174				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	68
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.73	$76.87	$83.00	$89.14	$95.27	$74.68	See Web	
Part No. PE3C6229				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	69
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.73	$76.87	$83.00	$89.14	$95.27	$74.67	See Web	

4.3-10 MALE TO 4.3-10 FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7829				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	70
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.41	$76.13	$79.86	$83.59	$87.31	$74.79	See Web	

Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

4.3-10 MALE TO 4.3-10 FEMALE 4 HOLE FLANGE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7830				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		71
12"	18"	24"	36"	48"	60"	Custom Len.	
$69.11	Call	$72.84	$76.57	$80.29	$84.02	See Web	

4.3-10 MALE TO 7/16 DIN MALE

Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4135				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	72
12"	24"	36"	48"	60"	50CM	Custom Len.	
$104.15	$108.74	$114.79	$120.84	$126.89	$106.57	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6184				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	73
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.80	$72.94	$79.07	$85.21	$91.34	$70.71	See Web	
Part No. PE3C6186				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	74
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.80	$72.94	$79.07	$85.21	$91.34	$70.71	See Web	

SPP-500-LLPL Coax, 50 Ohm

Part No. PE3C6365				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.5" dia.			75
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.87	$71.16	$81.44	$91.72	$101.99	$67.45	See Web	

SPO-375 Coax, 50 Ohm

Part No. PE3C6500				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			76
12"	24"	36"	48"	60"	50CM	Custom Len.	
$76.86	$80.01	$83.18	$86.33	$89.47	$78.89	See Web	

SPF-375 Coax, 50 Ohm

Part No. PE3C6506				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.435" dia.			77
12"	24"	36"	48"	60"	50CM	Custom Len.	
$76.86	$81.10	$85.34	$89.58	$93.81	$79.59	See Web	

SPO-500 Coax, 50 Ohm

Part No. PE3C6512				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.53" dia.			78
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.17	$56.76	$60.18	$62.94	$66.01	$55.66	See Web	

SPF-500 Coax, 50 Ohm

Part No. PE3C6515				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.			79
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.98	$59.37	$63.76	$68.14	$72.53	$57.78	See Web	

4.3-10 MALE TO 7/16 DIN MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6236				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	80
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.05	$78.19	$84.33	$90.47	$96.60	$75.97	See Web	
Part No. PE3C6238				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	81
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.05	$78.19	$84.33	$90.47	$96.60	$75.97	See Web	

4.3-10 MALE TO 7/16 DIN FEMALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5853				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			82
12"	24"	36"	48"	60"	50CM	Custom Len.	
$98.79	$104.93	$109.52	$115.57	$121.62	$102.73	See Web	
Part No. PE3C6230				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	83
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.80	$72.94	$79.07	$85.21	$91.34	$70.71	See Web	
Part No. PE3C6232				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	84
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.80	$72.94	$79.07	$85.21	$91.34	$70.71	See Web	

SPP-375-LLPL Coax, 50 Ohm

Part No. PE3C6381				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.402" dia.			85
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.90	Call	$75.89	$83.88	$91.88	$65.02	See Web	

SPO-375 Coax, 50 Ohm

Part No. PE3C6501				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			86
12"	24"	36"	48"	60"	50CM	Custom Len.	
$71.61	$74.76	$77.92	$81.07	$84.22	$73.63	See Web	

SPF-375 Coax, 50 Ohm

Part No. PE3C6507				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.435" dia.			87
12"	24"	36"	48"	60"	50CM	Custom Len.	
$71.61	$75.85	$80.09	$84.33	$88.55	$74.33	See Web	

4.3-10 MALE TO N MALE

Low Loss Flexible Cable Assemblies

LMR-240-UF Coax, 50 Ohm

Part No. PE3C7907				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft		88
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.29	$54.96	$56.12	$57.29	$58.45	$53.86	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6221				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	89
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.18	$70.31	$76.45	$82.58	$88.72	$68.09	See Web	
Part No. PE3C6223				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	90
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.18	$70.31	$76.45	$82.58	$88.72	$68.09	See Web	

SPP-375-LLPL Coax, 50 Ohm

Part No. PE3C6382				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.402" dia.			91
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.84	$71.82	$79.82	$87.82	$95.81	$68.95	See Web	

4.3-10 MALE TO N MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6228				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	92
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.80	$72.94	$79.07	$85.21	$91.34	$70.71	See Web	
Part No. PE3C6243				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	93
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.80	$72.94	$79.07	$85.21	$91.34	$70.71	See Web	

4.3-10 MALE TO N FEMALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6220				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	94
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.18	$70.31	$76.45	$82.58	$88.72	$68.09	See Web	
Part No. PE3C6225				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	95
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.18	$70.31	$76.45	$82.58	$88.72	$68.09	See Web	

SPO-375 Coax, 50 Ohm

Part No. PE3C6499				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			96
12"	24"	36"	48"	60"	50CM	Custom Len.	
$71.61	$74.76	$77.92	$81.07	$84.22	$73.63	See Web	

SPF-375 Coax, 50 Ohm

Part No. PE3C6505				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.435" dia.			97
12"	24"	36"	48"	60"	50CM	Custom Len.	
$71.61	$75.85	$80.09	$84.33	$88.55	$74.33	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

4.3-10 MALE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6219				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	98
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.18	$70.31	$76.45	$82.58	$88.72	$68.09	See Web	

Part No. PE3C6226				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	99
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.18	$70.31	$76.45	$82.58	$88.72	$68.09	See Web	

4.3-10 MALE TO QMA MALE

Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5865				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	1
12"	24"	36"	48"	60"	50CM	Custom Len.	
$86.90	$93.04	$99.17	$105.29	$109.88	$90.82	See Web	

4.3-10 MALE TO QMA MALE RIGHT ANGLE

Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5871				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	2
12"	24"	36"	48"	60"	50CM	Custom Len.	
$89.29	$95.42	$101.56	$107.69	$112.25	$93.21	See Web	

4.3-10 MALE TO QMA FEMALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5859				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			3
12"	24"	36"	48"	60"	50CM	Custom Len.	
$82.94	$89.07	$95.21	$101.34	$107.48	$86.88	See Web	

4.3-10 MALE TO SMA MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5884				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			4
12"	24"	36"	48"	60"	50CM	Custom Len.	
$78.96	$85.09	$91.22	$97.36	$103.49	$82.88	See Web	

Part No. PE3C6246				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	5
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.92	$65.05	$71.19	$77.32	$83.46	$62.84	See Web	

Part No. PE3C6247				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	6
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.92	$65.05	$71.19	$77.32	$83.46	$62.84	See Web	

4.3-10 MALE TO SMA MALE RIGHT ANGLE

Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5889				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	7
12"	24"	36"	48"	60"	50CM	Custom Len.	
$80.55	$86.69	$92.82	$98.95	$105.10	$84.48	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6248				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	8
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.18	$70.31	$76.45	$82.58	$88.72	$68.09	See Web	

Part No. PE3C6250				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	9
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.18	$70.31	$76.45	$82.58	$88.72	$68.09	See Web	

4.3-10 MALE TO SMA FEMALE

Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5878				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	10
12"	24"	36"	48"	60"	50CM	Custom Len.	
$79.75	$85.89	$92.02	$98.16	$104.29	$83.68	See Web	

4.3-10 MALE TO NEX10 MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6261				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	11
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.74	$78.88	$85.01	$91.15	$97.28	$76.66	See Web	

Part No. PE3C6263				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	12
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.74	$78.88	$85.01	$91.15	$97.28	$76.66	See Web	

4.3-10 MALE RIGHT ANGLE TO 4.3-10 MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4147				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			13
12"	24"	36"	48"	60"	50CM	Custom Len.	
$107.77	$113.82	$119.88	$125.93	$131.98	$111.66	See Web	

4.3-10 MALE RIGHT ANGLE TO 4.3-10 MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7831				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		14
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.61	$78.34	$82.06	$85.79	$89.52	$77.00	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4146				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			15
12"	24"	36"	48"	60"	50CM	Custom Len.	
$115.38	$121.43	$127.47	$133.52	$139.57	$119.25	See Web	

Part No. PE3C6177				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	16
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.37	$79.50	$85.64	$91.77	$97.91	$77.29	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C6339				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			17
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.51	$71.80	$74.09	$76.38	$78.66	$70.98	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C6354				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			18
12"	24"	36"	48"	60"	50CM	Custom Len.	
$70.26	$73.26	$76.27	$79.30	$82.31	$72.18	See Web	

4.3-10 MALE RIGHT ANGLE TO 4.3-10 FEMALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7832				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		19
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.51	$77.24	$80.96	$84.69	$88.41	$75.90	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6227				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	20
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.05	$78.19	$84.33	$90.47	$96.60	$75.97	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

SPO-250 Coax, 50 Ohm

Part No. PE3C6332				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			21
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.21	$70.50	$72.78	$75.05	$77.34	$69.68	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C6349				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			22
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.93	$71.95	$74.97	$77.98	$81.00	$70.87	See Web	

4.3-10 MALE RIGHT ANGLE TO 4.3-10 FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7833				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		23
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.61	$78.34	$82.06	$85.79	$89.52	$77.00	See Web	

4.3-10 MALE RIGHT ANGLE TO 4.3-10 FEMALE 4 HOLE FLANGE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7834				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		24
12"	24"	36"	48"	60"	50CM	Custom Len.	
$71.31	$75.03	$78.76	$82.50	$86.22	$73.69	See Web	

4.3-10 MALE RIGHT ANGLE TO 7/16 DIN MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6185				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	25
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.12	$74.24	$80.38	$86.51	$92.65	$72.03	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C6340				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			26
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.26	$66.54	$68.83	$71.12	$73.41	$65.72	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C6355				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			27
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.00	$68.01	$71.03	$74.05	$77.06	$66.92	See Web	

4.3-10 MALE RIGHT ANGLE TO 7/16 DIN MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6237				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	28
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.37	$79.50	$85.64	$91.77	$97.91	$77.29	See Web	

4.3-10 MALE RIGHT ANGLE TO 7/16 DIN FEMALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6231				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	29
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.12	$74.24	$80.38	$86.51	$92.65	$72.03	See Web	

4.3-10 MALE RIGHT ANGLE TO N MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6222				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	30
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.50	$71.62	$77.75	$83.89	$90.02	$69.41	See Web	

4.3-10 MALE RIGHT ANGLE TO N MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6242				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	31
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.12	$74.24	$80.38	$86.51	$92.65	$72.03	See Web	

4.3-10 MALE RIGHT ANGLE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6239				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	32
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.50	$71.62	$77.75	$83.89	$90.02	$69.41	See Web	

4.3-10 MALE RIGHT ANGLE TO SMA MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6245				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	33
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.24	$66.37	$72.49	$78.63	$84.76	$64.16	See Web	

4.3-10 MALE RIGHT ANGLE TO SMA MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6249				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	34
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.50	$71.62	$77.75	$83.89	$90.02	$69.41	See Web	

4.3-10 MALE RIGHT ANGLE TO NEX10 MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6262				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	35
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.06	$80.19	$86.33	$92.46	$98.60	$77.97	See Web	

4.3-10 FEMALE TO 4.3-10 FEMALE

Corrugated Cable Assemblies

SPO-250 Coax, 50 Ohm

Part No. PE3C6331				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			36
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.89	$69.18	$71.46	$73.75	$76.04	$68.35	See Web	

Low PIM Corrugated Cable Assemblies

SPF-250 Coax, 50 Ohm

Part No. PE3C6348				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			37
12"	24"	36"	48"	60"	50CM	Custom Len.	
$67.62	$70.64	$73.65	$76.67	$79.69	$69.55	See Web	

4.3-10 FEMALE TO 7/16 DIN MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6233				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	38
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.80	$72.94	$79.07	$85.21	$91.34	$70.71	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C6333				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			39
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.96	$65.24	$67.52	$69.81	$72.09	$64.42	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

SPF-250 Coax, 50 Ohm

Part No. PE3C6350				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			40
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.68	$66.71	$69.72	$72.73	$75.76	$65.61	See Web	

4.3-10 FEMALE TO 7/16 DIN MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6235				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	41
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.05	$78.19	$84.33	$90.47	$96.60	$75.97	See Web	

4.3-10 FEMALE TO N MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5837				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			42
12"	24"	36"	48"	60"	50CM	Custom Len.	
$94.82	$100.95	$107.09	$111.64	$117.69	$98.74	See Web	
Part No. PE3C6240				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	43
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.18	$70.31	$76.45	$82.58	$88.72	$68.09	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C6336				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			44
12"	24"	36"	48"	60"	50CM	Custom Len.	
$57.70	$59.99	$62.27	$64.55	$66.84	$59.16	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C6351				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			45
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.42	$61.45	$64.46	$67.47	$70.50	$60.36	See Web	

4.3-10 FEMALE TO N MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6241				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	46
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.80	$72.94	$79.07	$85.21	$91.34	$70.71	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C6337				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			47
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.96	$65.24	$67.52	$69.81	$72.09	$64.42	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C6352				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			48
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.68	$66.71	$69.72	$72.73	$75.76	$65.61	See Web	

4.3-10 FEMALE TO QMA MALE

Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5838				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	49
12"	24"	36"	48"	60"	50CM	Custom Len.	
$90.84	$96.98	$103.11	$107.73	$113.78	$94.79	See Web	

4.3-10 FEMALE TO SMA MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5839				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			50
12"	24"	36"	48"	60"	50CM	Custom Len.	
$82.91	$89.04	$95.17	$101.31	$107.44	$86.84	See Web	

4.3-10 FEMALE TO NEX10 MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6264				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	51
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.74	$78.88	$85.01	$91.15	$97.28	$76.66	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C6338				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			52
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.89	$71.18	$73.47	$75.76	$78.02	$70.36	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C6353				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			53
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.62	$72.63	$75.65	$78.67	$81.69	$71.55	See Web	

7/16 DIN MALE TO 4.3-10 FEMALE

Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5836				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	54
12"	24"	36"	48"	60"	50CM	Custom Len.	
$102.76	$107.38	$113.43	$119.48	$125.53	$106.68	See Web	

7/16 DIN MALE TO 7/16 DIN MALE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE37952				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	55
36"	48"	60"	72"	120"	-	Custom Len.	
$93.20	$94.00	$94.73	$95.46	$98.49	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE37953				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	56
36"	48"	60"	72"	120"	-	Custom Len.	
$113.70	$114.74	$115.75	$116.75	$120.73	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE37954				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	57
36"	48"	60"	72"	120"	-	Custom Len.	
$153.66	$155.03	$156.39	$157.75	$163.21	-	See Web	

PE-C600 Coax, 50 Ohm

Part No. PE37955				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.7 dB/100ft	900 W	58
36"	48"	60"	72"	120"	-	Custom Len.	
$184.28	$176.55	$179.24	$181.92	$192.65	-	See Web	

LMR-400 Coax, 50 Ohm

Part No. PE3W03530				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		59
12"	24"	36"	48"	60"	50CM	Custom Len.	
$96.36	$97.74	$99.11	$100.48	$101.85	$97.25	See Web	

Low PIM Formable Cable Assemblies

PE-SR401FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2013				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.276" dia.			60
100CM	200CM	-	-	-	-	Custom Len.	
$190.93	$221.72	-	-	-	-	See Web	

PE-SR402FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2003				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.			61
100CM	200CM	-	-	-	-	Custom Len.	
$139.09	$161.25	-	-	-	-	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7835				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		62
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.71	$68.44	$72.17	$75.90	$79.62	$67.09	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4130				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	63
12"	24"	36"	48"	60"	50CM	Custom Len.	
$106.71	$111.28	$117.33	$123.37	$129.42	$108.81	See Web	

Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

Part No. PE3C6181				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	64
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.86	$69.00	$75.12	$81.26	$87.40	$66.78	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C6341				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			65
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.01	$61.29	$63.58	$65.86	$68.15	$60.46	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C6356				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			66
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.74	$62.75	$65.78	$68.79	$71.80	$61.67	See Web	

SPO-375 Coax, 50 Ohm

Part No. PE3C6502				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			67
12"	24"	36"	48"	60"	50CM	Custom Len.	
$76.86	$80.01	$83.18	$86.33	$89.47	$78.89	See Web	

SPF-375 Coax, 50 Ohm

Part No. PE3C6508				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.435" dia.			68
12"	24"	36"	48"	60"	50CM	Custom Len.	
$76.86	$81.10	$85.34	$89.58	$93.81	$79.59	See Web	

SPO-500 Coax, 50 Ohm

Part No. PE3C6511				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.53" dia.			69
12"	24"	36"	48"	60"	50CM	Custom Len.	
$50.20	$53.31	$55.91	$58.98	$62.07	$52.19	See Web	

SPF-500 Coax, 50 Ohm

Part No. PE3C6514				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.			70
12"	24"	36"	48"	60"	50CM	Custom Len.	
$51.51	$55.61	$59.80	$64.20	$68.58	$54.35	See Web	

Standard Formable Cable Assemblies

PE-SR401FL Coax, 50 Ohm

Part No. PE36140				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	71
12"	24"	36"	48"	60"	72"	Custom Len.	
$335.14	$351.34	$367.55	$383.76	$399.92	$416.13	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE36144				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	72
12"	24"	36"	48"	60"	72"	Custom Len.	
$320.30	$328.23	$336.17	$344.06	$351.99	$359.86	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE35283				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	73
12"	24"	36"	48"	60"	-	Custom Len.	
$264.54	$267.41	$270.20	$273.00	$275.86	-	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3183				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	74
12"	24"	36"	48"	60"	72"	Custom Len.	
$258.20	$259.01	$259.80	$260.59	$261.39	$262.20	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3189				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		75
12"	24"	36"	48"	60"	72"	Custom Len.	
$114.41	$120.64	$126.84	$133.06	$139.28	$145.48	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3199				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	9 dB/100ft	190 W	76
12"	24"	36"	48"	60"	72"	Custom Len.	
$270.32	$272.13	$273.90	$275.72	$277.55	$279.37	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3185				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	77
12"	24"	36"	48"	60"	72"	Custom Len.	
$286.00	$293.93	$301.89	$328.96	$317.76	$325.71	See Web	

RG217/U Coax, 50 Ohm

Part No. PE36134				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.	5.8 dB/100ft	260 W	78
12"	24"	36"	48"	60"	72"	Custom Len.	
$346.42	$351.20	$355.96	$360.74	$365.50	$370.28	See Web	

RG218/U Coax, 50 Ohm

Part No. PE35900				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.87" dia.	3.8 dB/100ft	560 W	79
12"	24"	36"	48"	60"	72"	Custom Len.	
$377.59	$390.05	$402.53	$414.98	$454.13	$439.92	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3192				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	80
12"	24"	36"	48"	60"	72"	Custom Len.	
$106.53	$108.25	$111.37	$114.56	$117.75	$120.85	See Web	

RG225/U Coax, 50 Ohm

Part No. PE36136				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	81
12"	24"	36"	48"	60"	72"	Custom Len.	
$297.15	$332.47	$367.80	$403.14	$438.45	$473.80	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3205				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	82
12"	24"	36"	48"	60"	72"	Custom Len.	
$295.46	$177.26	$195.04	$213.87	$232.00	$250.14	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34360				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	83
12"	24"	36"	48"	60"	72"	Custom Len.	
$116.07	$123.66	$131.26	$138.89	$146.51	$154.11	See Web	

Standard Semi-Rigid Cable Assemblies

RG401/U Coax, 50 Ohm

Part No. PE36138				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	84
12"	24"	36"	48"	60"	72"	Custom Len.	
$342.02	$365.07	$388.15	$411.25	$434.37	Call	See Web	

RG402/U Coax, 50 Ohm

Part No. PE36142				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	85
12"	24"	36"	48"	60"	72"	Custom Len.	
$320.10	$327.79	$335.46	$343.13	$350.82	$358.49	See Web	

7/16 DIN MALE TO 7/16 DIN MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE37956				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	86
36"	48"	60"	72"	120"	-	Custom Len.	
$87.99	$88.72	$89.52	$90.24	$93.27	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE37957				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	87
36"	48"	60"	72"	120"	-	Custom Len.	
$136.55	$137.58	$138.57	$139.54	$143.58	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE37958				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	88
36"	48"	60"	72"	120"	-	Custom Len.	
$170.76	$172.19	$173.62	$175.05	$180.76	-	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7836				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		89
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.66	$73.94	$77.67	$81.39	$85.12	$72.59	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6188				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	90
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.12	$74.24	$80.38	$86.51	$92.65	$72.03	See Web	

Standard Flexible Cable Assemblies

RG214/U Coax, 50 Ohm

Part No. PE38584				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	91
12"	24"	36"	48"	60"	-	Custom Len.	
$309.73	$317.67	$325.61	$333.55	$341.49	-	See Web	

RG217/U Coax, 50 Ohm

Part No. PE37600				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.	5.8 dB/100ft	260 W	92
12"	24"	36"	48"	60"	-	Custom Len.	
$387.95	$392.73	$397.49	$402.28	$432.10	-	See Web	

RG393/U Coax, 50 Ohm

Part No. PE36657				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W	93
12"	24"	36"	48"	60"	-	Custom Len.	
$337.52	$355.30	$351.94	$368.73	$410.05	-	See Web	

PE-1/2 Helical Coax, 50 Ohm

Part No. PE37973				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.54" dia.			94
36"	72"	-	-	-	-	Custom Len.	
$170.30	$198.83	-	-	-	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

7/16 DIN MALE TO 7/16 DIN FEMALE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm — 95

Part No. PE37960				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W
36"	48"	60"	72"	120"	-	Custom Len.
$87.99	$88.72	$89.52	$90.24	$93.27	-	See Web

PE-C240 Coax, 50 Ohm — 96

Part No. PE37961				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W
36"	48"	60"	72"	120"	-	Custom Len.
$130.03	$131.10	$132.06	$133.02	$137.07	-	See Web

PE-C400 Coax, 50 Ohm — 97

Part No. PE37962				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W
36"	48"	60"	72"	120"	-	Custom Len.
$165.20	$166.54	$167.89	$169.29	$174.74	-	See Web

PE-C600 Coax, 50 Ohm — 98

Part No. PE37963				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.7 dB/100ft	900 W
36"	48"	60"	72"	120"	-	Custom Len.
$180.41	$183.01	$185.62	$188.14	$198.54	-	See Web

Low PIM Formable Cable Assemblies

PE-SR401FLJ Low PIM Coax, 50 Ohm — 99

Part No. PE3C2015				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.276" dia.		
100CM	200CM	-	-	-	-	Custom Len.
$190.93	$221.72	-	-	-	-	See Web

PE-SR402FLJ Low PIM Coax, 50 Ohm — 1

Part No. PE3C2004				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.161" dia.		
100CM	200CM	-	-	-	-	Custom Len.
$115.49	$123.91	-	-	-	-	See Web

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm — 2

Part No. PE3C7837				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$64.71	$68.44	$72.17	$75.90	$79.62	$67.09	See Web

SPP-250-LLPL Coax, 50 Ohm — 3

Part No. PE3C5855				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$102.76	$107.38	$113.43	$119.48	$125.53	$106.68	See Web

— 4

Part No. PE3C6182				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$62.86	$69.00	$75.12	$81.26	$87.40	$66.78	See Web

SPO-375 Coax, 50 Ohm — 5

Part No. PE3C6503				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.43" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$71.61	$74.76	$77.92	$81.07	$84.22	$73.63	See Web

SPF-375 Coax, 50 Ohm — 6

Part No. PE3C6509				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.435" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$71.61	$75.85	$80.09	$84.33	$88.55	$74.33	See Web

Standard Flexible Cable Assemblies

RG393/U Coax, 50 Ohm — 7

Part No. PE37450				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W
12"	24"	36"	48"	60"	-	Custom Len.
$306.14	$322.90	$339.67	$356.44	$397.04	-	See Web

PE-1/2 Helical Coax, 50 Ohm — 8

Part No. PE37972				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.54" dia.		
36"	72"	-	-	-	-	Custom Len.
$156.16	$188.28	-	-	-	-	See Web

7/16 DIN MALE TO 7/16 DIN FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm — 9

Part No. PE3C7838				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft	
12"	50CM	24"	36"	48"	60"	Custom Len.
$77.35	$79.74	$81.08	$84.81	$88.53	$92.27	See Web

7/16 DIN MALE TO N MALE

Low Loss Flexible Cable Assemblies

LMR-400-UF Coax, 50 Ohm — 10

Part No. PE3W03271				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	5 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$101.85	$104.73	$107.62	$108.97	$111.82	$103.70	See Web

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm — 11

Part No. PE3C6192				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$60.24	$66.37	$72.49	$78.63	$84.76	$64.16	See Web

SPO-250 Coax, 50 Ohm — 12

Part No. PE3C6342				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$54.24	$56.04	$58.32	$60.61	$62.89	$55.21	See Web

SPF-250 Coax, 50 Ohm — 13

Part No. PE3C6357				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$54.49	$57.50	$60.53	$63.54	$66.54	$56.42	See Web

SPP-500-LLPL Coax, 50 Ohm — 14

Part No. PE3C6369				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.5" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$54.30	$64.58	$74.87	$85.15	$95.43	$60.88	See Web

Standard Semi-Rigid Cable Assemblies

RG401/U Coax, 50 Ohm — 15

Part No. PE36174				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	1,400 W
12"	24"	36"	48"	60"	72"	Custom Len.
$239.16	$262.26	$285.36	$308.41	$331.51	Call	See Web

7/16 DIN MALE TO N MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm — 16

Part No. PE3C6193				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$62.86	$69.00	$75.12	$81.26	$87.40	$66.78	See Web

SPO-250 Coax, 50 Ohm — 17

Part No. PE3C6343				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$59.01	$61.29	$63.58	$65.86	$68.15	$60.46	See Web

SPF-250 Coax, 50 Ohm — 18

Part No. PE3C6358				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$59.74	$62.75	$65.78	$68.79	$71.80	$61.67	See Web

7/16 DIN MALE TO N FEMALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm — 19

Part No. PE3C6190				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$60.24	$66.37	$72.49	$78.63	$84.76	$64.16	See Web

7/16 DIN MALE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm — 20

Part No. PE3C6191				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$60.24	$66.37	$72.49	$78.63	$84.76	$64.16	See Web

7/16 DIN MALE TO QMA MALE

Low PIM Corrugated Cable Assemblies

Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5867				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	21
1 piece price shown. See web or call for volume pricing.				0.28" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$90.84	$96.98	$103.11	$107.73	$113.78	$94.79	See Web	

7/16 DIN MALE TO QMA MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5873				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	22
1 piece price shown. See web or call for volume pricing.				0.28" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$93.23	$99.36	$105.50	$110.08	$116.13	$97.17	See Web	

7/16 DIN MALE TO QMA FEMALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5861				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	23
1 piece price shown. See web or call for volume pricing.				0.28" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$86.90	$93.04	$99.17	$105.29	$109.88	$90.82	See Web	

7/16 DIN MALE TO SC MALE

Standard Flexible Cable Assemblies

RG393/U Coax, 50 Ohm

Part No. PE37497				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	24
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$224.61	$241.88	$259.15	$276.42	$293.69	$235.68	See Web	

7/16 DIN MALE TO SMA MALE

Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5886				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	25
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$82.91	$89.04	$95.17	$101.31	$107.44	$86.84	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6194				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	26
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.98	$61.12	$67.26	$73.38	$79.51	$58.90	See Web	

7/16 DIN MALE TO SMA MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5891				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	27
1 piece price shown. See web or call for volume pricing.				0.28" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$84.50	$90.64	$96.77	$102.91	$107.53	$88.44	See Web	

Part No. PE3C6195				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	28
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.24	$66.37	$72.49	$78.63	$84.76	$64.16	See Web	

7/16 DIN MALE TO SMA FEMALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5880				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	29
1 piece price shown. See web or call for volume pricing.				0.28" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$83.72	$89.85	$95.98	$102.12	$106.75	$87.64	See Web	

7/16 DIN MALE TO NEX10 MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6251				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	30
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.80	$74.94	$81.07	$87.20	$93.34	$72.72	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C6344				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	31
1 piece price shown. See web or call for volume pricing.				0.303" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.96	$67.25	$69.51	$71.80	$74.09	$66.41	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C6359				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	32
1 piece price shown. See web or call for volume pricing.				0.303" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.68	$68.70	$71.72	$74.73	$77.74	$67.61	See Web	

7/16 DIN MALE RIGHT ANGLE TO 7/16 DIN MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4131				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	33
1 piece price shown. See web or call for volume pricing.				0.28" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$117.91	$123.97	$130.02	$136.07	$142.12	$121.81	See Web	

7/16 DIN MALE RIGHT ANGLE TO 7/16 DIN MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7839				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	34
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.61	$78.34	$82.06	$85.79	$89.52	$77.00	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4144				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	35
1 piece price shown. See web or call for volume pricing.				0.28" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$130.58	$136.53	$142.68	$148.73	$154.78	$134.47	See Web	

Part No. PE3C6189				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	36
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.37	$79.50	$85.64	$91.77	$97.91	$77.29	See Web	

7/16 DIN MALE RIGHT ANGLE TO 7/16 DIN FEMALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7840				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	37
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		
12"	50CM	24"	36"	48"	60"	Custom Len.	
$69.66	$72.04	$73.39	$77.12	$80.84	$84.57	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6183				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	38
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.12	$74.24	$80.38	$86.51	$92.65	$72.03	See Web	

7/16 DIN MALE RIGHT ANGLE TO 7/16 DIN FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7841				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	39
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$82.30	$86.03	$89.75	$93.49	$97.22	$84.69	See Web	

7/16 DIN MALE RIGHT ANGLE TO N MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6198				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	40
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.50	$71.62	$77.75	$83.89	$90.02	$69.41	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

7/16 DIN MALE RIGHT ANGLE TO N MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6199				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	41
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.12	$74.24	$80.38	$86.51	$92.65	$72.03	See Web	

7/16 DIN MALE RIGHT ANGLE TO N FEMALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6196				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	42
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.50	$71.62	$77.75	$83.89	$90.02	$69.41	See Web	

7/16 DIN MALE RIGHT ANGLE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6197				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	43
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.50	$71.62	$77.75	$83.89	$90.02	$69.41	See Web	

7/16 DIN MALE RIGHT ANGLE TO NEX10 MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6252				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	44
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.06	$80.19	$86.33	$92.46	$98.60	$77.97	See Web	

7/16 DIN FEMALE TO 7/16 DIN FEMALE

Corrugated Cable Assemblies

SPO-375 Coax, 50 Ohm

Part No. PE3C6504				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			45
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.36	$69.50	$72.66	$75.82	$78.97	$68.37	See Web	

Low PIM Corrugated Cable Assemblies

SPP-375-LLPL Coax, 50 Ohm

Part No. PE3C6383				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.402" dia.			46
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.65	$62.63	$70.63	$78.62	$86.62	$59.76	See Web	

SPF-375 Coax, 50 Ohm

Part No. PE3C6510				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.435" dia.			47
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.36	$70.59	$74.83	$79.07	$83.31	$69.08	See Web	

7/16 DIN FEMALE TO N MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5856				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			48
12"	24"	36"	48"	60"	50CM	Custom Len.	
$94.82	$100.95	$107.09	$111.64	$117.69	$98.74	See Web	
Part No. PE3C6224				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	49
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.24	$66.37	$72.49	$78.63	$84.76	$64.16	See Web	

SPP-375-LLPL Coax, 50 Ohm

Part No. PE3C6384				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.402" dia.			50
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.58	$66.57	$74.58	$82.57	$90.56	$63.70	See Web	

7/16 DIN FEMALE TO N MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6244				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	51
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.86	$69.00	$75.12	$81.26	$87.40	$66.78	See Web	

7/16 DIN FEMALE TO QMA MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5857				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			52
12"	24"	36"	48"	60"	50CM	Custom Len.	
$90.84	$96.98	$103.11	$107.73	$113.78	$94.79	See Web	

7/16 DIN FEMALE TO SMA MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5858				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			53
12"	24"	36"	48"	60"	50CM	Custom Len.	
$82.91	$89.04	$95.17	$101.31	$107.44	$86.84	See Web	

7/16 DIN FEMALE TO NEX10 MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6260				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	54
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.80	$74.94	$81.07	$87.20	$93.34	$72.72	See Web	

10-32 MALE TO 10-32 MALE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36520				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	55
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.99	$73.62	$71.14	$74.94	$75.58	$76.22	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36522				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	56
12"	24"	36"	48"	60"	72"	Custom Len.	
$98.10	$99.14	$106.32	$101.27	$107.23	$103.37	See Web	

RG316/U Coax, 50 Ohm

Part No. PE36524				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	57
12"	24"	36"	48"	60"	72"	Custom Len.	
$74.59	$77.75	$80.93	$89.57	$93.07	$96.58	See Web	

10-32 MALE TO 10-32 MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36526				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	58
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.84	$73.89	$74.37	$74.86	$75.32	$75.81	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36528				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	59
12"	24"	36"	48"	60"	72"	Custom Len.	
$95.53	$96.58	$97.62	$98.68	$99.73	$100.78	See Web	

RG316/U Coax, 50 Ohm

Part No. PE36530				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	60
12"	24"	36"	48"	60"	72"	Custom Len.	
$74.91	$78.09	$81.26	$84.44	$87.63	$90.79	See Web	

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

See Our Website For Current Pricing & Real-Time Stock Availability!

10-32 MALE TO BNC MALE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C3275				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	61
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.45	$56.08	$56.73	$57.40	$58.04	$58.69	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36540				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	62
12"	24"	36"	48"	60"	72"	Custom Len.	
$90.49	$91.65	$92.81	$88.52	$89.59	$90.63	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C3424				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	63
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.81	$56.75	$59.72	$62.89	$67.33	$70.82	See Web	

10-32 MALE RIGHT ANGLE TO 10-32 MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36532				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	64
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.22	$72.74	$73.21	$73.68	$74.19	$74.67	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36534				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	65
12"	24"	36"	48"	60"	72"	Custom Len.	
$104.40	$105.46	$106.51	$107.57	$107.11	$114.98	See Web	

RG316/U Coax, 50 Ohm

Part No. PE36536				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	66
12"	24"	36"	48"	60"	72"	Custom Len.	
$75.04	$78.37	$81.66	$84.96	$88.25	$97.05	See Web	

10-32 MALE RIGHT ANGLE TO BNC FEMALE

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C2998				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		67
12"	24"	36"	48"	60"	50CM	Custom Len.	
$53.97	$54.24	$54.63	$55.40	$56.16	$54.07	See Web	

10-32 MALE RIGHT ANGLE TO SMP FEMALE

Flexible Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C7720				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	68
12"	24"	36"	48"	60"	50CM	Custom Len.	
$77.84	$79.09	$80.35	$81.60	$82.85	$77.39	See Web	

10-32 FEMALE TO BNC MALE

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3W03496				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	69
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.09	$75.23	$76.35	$77.47	$78.61	$74.81	See Web	

BMA PLUG BULKHEAD TO BMA PLUG BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4899				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	70
6"	12"	24"	36"	60"	-	Custom Len.	
$77.55	$81.58	$89.64	$97.70	$112.25	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4844				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	71
6"	12"	24"	36"	60"	-	Custom Len.	
$79.57	$83.72	$91.98	$100.25	$115.18	-	See Web	

Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4936				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	72
6"	12"	24"	36"	60"	-	Custom Len.	
$118.42	$119.96	$122.98	$126.02	$132.10	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4950				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	73
6"	12"	24"	36"	60"	-	Custom Len.	
$93.03	$96.74	$104.17	$110.05	$124.74	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4921				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		74
6"	12"	24"	36"	60"	-	Custom Len.	
$112.13	$112.53	$113.33	$114.13	$115.74	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4872				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	75
6"	12"	24"	36"	60"	-	Custom Len.	
$79.10	$82.77	$90.09	$68.84	$110.53	-	See Web	

BMA PLUG BULKHEAD TO BMA JACK

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4904				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	76
6"	12"	24"	36"	60"	-	Custom Len.	
$136.24	$140.20	$148.16	$156.10	$171.99	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4852				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	77
6"	12"	24"	36"	60"	-	Custom Len.	
$125.41	$129.49	$137.66	$145.81	$162.13	-	See Web	

Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4940				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	78
6"	12"	24"	36"	60"	-	Custom Len.	
$150.87	$152.42	$155.44	$158.48	$164.56	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4953				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	79
6"	12"	24"	36"	60"	-	Custom Len.	
$165.93	$169.61	$176.94	$184.27	$198.95	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4925				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		80
6"	12"	24"	36"	60"	-	Custom Len.	
$144.59	$144.98	$145.79	$146.58	$148.19	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4879				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	81
6"	12"	24"	36"	60"	-	Custom Len.	
$124.96	$128.56	$135.78	$143.01	$157.48	-	See Web	

BMA PLUG BULKHEAD TO BMA JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4851				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	82
6"	12"	24"	36"	60"	-	Custom Len.	
$100.44	$104.58	$111.29	$119.46	$135.76	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4878				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	83
6"	12"	24"	36"	60"	-	Custom Len.	
$99.97	$103.64	$109.42	$116.65	$131.12	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

BMA PLUG BULKHEAD TO BMA JACK 2 HOLE FLANGE

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4903				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	84
6"	12"	24"	36"	60"	-	Custom Len.	
$92.95	$96.99	$105.05	$111.54	$127.42	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4850				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	85
6"	12"	24"	36"	60"	-	Custom Len.	
$106.75	$109.37	$117.53	$125.67	$142.00	-	See Web	

Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4939				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	86
6"	12"	24"	36"	60"	-	Custom Len.	
$113.64	$115.18	$118.20	$121.24	$127.33	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4924				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		87
6"	12"	24"	36"	60"	-	Custom Len.	
$107.36	$107.75	$108.56	$109.36	$110.95	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4877				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	88
6"	12"	24"	36"	60"	-	Custom Len.	
$106.31	$108.42	$115.64	$122.87	$137.35	-	See Web	

BMA PLUG BULKHEAD TO BMA JACK RIGHT ANGLE 2 HOLE FLANGE

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4905				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	89
6"	12"	24"	36"	60"	-	Custom Len.	
$123.15	$127.13	$135.09	$143.02	$158.91	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4853				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	90
6"	12"	24"	36"	60"	-	Custom Len.	
$118.17	$122.25	$130.40	$138.57	$154.89	-	See Web	

Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE3C4954				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	91
6"	12"	24"	36"	60"	-	Custom Len.	
$115.69	$119.37	$126.70	$134.02	$148.70	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4880				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	92
6"	12"	24"	36"	60"	-	Custom Len.	
$117.72	$121.33	$128.54	$135.77	$150.23	-	See Web	

BMA PLUG BULKHEAD TO BNC MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4918				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	93
6"	12"	24"	36"	60"	-	Custom Len.	
$76.77	$80.82	$88.87	$96.92	$111.48	-	See Web	

Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4949				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	94
6"	12"	24"	36"	60"	-	Custom Len.	
$76.12	$77.68	$80.75	$83.82	$89.99	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4963				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	95
6"	12"	24"	36"	60"	-	Custom Len.	
$64.10	$67.84	$75.26	$82.69	$97.57	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4935				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		96
6"	12"	24"	36"	60"	-	Custom Len.	
$69.73	$70.14	$70.96	$71.77	$73.38	-	See Web	

BMA PLUG BULKHEAD TO N MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4912				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	97
6"	12"	24"	36"	60"	-	Custom Len.	
$68.63	$72.66	$80.72	$88.78	$104.89	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4860				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	98
6"	12"	24"	36"	60"	-	Custom Len.	
$69.69	$73.82	$82.10	$90.36	$106.92	-	See Web	

Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4945				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	99
6"	12"	24"	36"	60"	-	Custom Len.	
$98.76	$87.93	$87.93	$91.01	$94.08	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4959				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	1
6"	12"	24"	36"	60"	-	Custom Len.	
$74.99	$78.72	$86.15	$93.59	$106.95	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4931				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		2
6"	12"	24"	36"	60"	-	Custom Len.	
$79.99	$80.40	$81.21	$82.03	$83.65	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4887				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	3
6"	12"	24"	36"	60"	-	Custom Len.	
$69.22	$72.89	$80.21	$87.54	$102.21	-	See Web	

BMA PLUG BULKHEAD TO SMA MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4906				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	4
6"	12"	24"	36"	60"	-	Custom Len.	
$60.17	$64.21	$72.27	$80.32	$96.44	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4854				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	5
6"	12"	24"	36"	60"	-	Custom Len.	
$62.06	$66.21	$74.47	$82.74	$99.30	-	See Web	

Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4942				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	6
6"	12"	24"	36"	60"	-	Custom Len.	
$79.75	$81.31	$84.37	$87.46	$93.63	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4955				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	7
6"	12"	24"	36"	60"	-	Custom Len.	
$69.06	$72.78	$80.21	$87.65	$102.52	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4927				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		8
6"	12"	24"	36"	60"	-	Custom Len.	
$73.36	$73.78	$74.60	$75.39	$77.02	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4881				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	9
6"	12"	24"	36"	60"	-	Custom Len.	
$61.60	$65.27	$72.59	$79.91	$94.58	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

BMA PLUG BULKHEAD TO SMA MALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4909				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	10
6"	12"	24"	36"	60"	-	Custom Len.	
$63.09	$67.12	$75.19	$83.24	$99.35	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4857				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	11
6"	12"	24"	36"	60"	-	Custom Len.	
$64.16	$68.28	$76.57	$84.84	$101.37	-	See Web	

Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4386				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	12
6"	12"	24"	36"	60"	-	Custom Len.	
$95.97	$97.52	$100.57	$103.66	$108.30	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4957				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	13
6"	12"	24"	36"	60"	-	Custom Len.	
$79.95	$83.67	$91.10	$98.53	$111.84	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4929				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		14
6"	12"	24"	36"	60"	-	Custom Len.	
$84.37	$86.06	$86.88	$86.37	$87.96	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4884				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	15
6"	12"	24"	36"	60"	-	Custom Len.	
$63.68	$67.35	$74.68	$82.01	$96.68	-	See Web	

BMA PLUG BULKHEAD TO SMP FEMALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4866				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	16
6"	12"	24"	36"	60"	-	Custom Len.	
$71.51	$75.64	$83.92	$92.19	$107.23	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4893				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	17
6"	12"	24"	36"	60"	-	Custom Len.	
$71.05	$74.71	$82.03	$89.36	$104.02	-	See Web	

BMA PLUG BULKHEAD TO SMP FEMALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4869				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	18
6"	12"	24"	36"	60"	-	Custom Len.	
$84.43	$88.56	$96.85	$105.12	$119.98	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4896				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	19
6"	12"	24"	36"	60"	-	Custom Len.	
$83.97	$87.64	$94.95	$102.28	$115.32	-	See Web	

BMA PLUG BULKHEAD TO TNC MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4915				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	20
6"	12"	24"	36"	60"	-	Custom Len.	
$65.14	$69.19	$77.25	$85.29	$101.42	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4863				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	21
6"	12"	24"	36"	60"	-	Custom Len.	
$66.21	$70.36	$78.62	$86.90	$103.44	-	See Web	

Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE3C4961				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	22
6"	12"	24"	36"	60"	-	Custom Len.	
$69.01	$72.73	$80.16	$87.60	$102.48	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4890				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	23
6"	12"	24"	36"	60"	-	Custom Len.	
$65.73	$69.41	$76.73	$84.06	$98.73	-	See Web	

BMA JACK TO BMA JACK

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4901				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	24
6"	12"	24"	36"	60"	-	Custom Len.	
$196.00	$199.96	$207.91	$215.86	$231.75	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4848				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	25
6"	12"	24"	36"	60"	-	Custom Len.	
$172.36	$176.44	$184.60	$192.76	$209.09	-	See Web	

Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4938				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	26
6"	12"	24"	36"	60"	-	Custom Len.	
$183.33	$184.86	$187.88	$190.93	$197.01	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4951				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	27
6"	12"	24"	36"	60"	-	Custom Len.	
$240.15	$243.83	$251.15	$258.49	$273.17	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4923				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		28
6"	12"	24"	36"	60"	-	Custom Len.	
$177.03	$177.43	$178.23	$179.04	$180.63	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4875				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	29
6"	12"	24"	36"	60"	-	Custom Len.	
$171.91	$175.52	$182.74	$189.97	$204.43	-	See Web	

BMA JACK TO BNC MALE

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4920				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	30
6"	12"	24"	36"	60"	-	Custom Len.	
$135.46	$139.45	$147.39	$155.34	$171.24	-	See Web	

Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4948				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	31
6"	12"	24"	36"	60"	-	Custom Len.	
$107.52	$109.06	$112.07	$115.12	$121.20	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4964				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	32
6"	12"	24"	36"	60"	-	Custom Len.	
$137.43	$141.10	$148.43	$155.76	$170.43	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4934				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		33
6"	12"	24"	36"	60"	-	Custom Len.	
$102.65	$103.06	$103.88	$104.68	$106.31	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

BMA JACK TO N MALE

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4914				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	34
6"	12"	24"	36"	60"	-	Custom Len.	
$127.42	$131.42	$139.35	$147.31	$163.18	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4862				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	35
6"	12"	24"	36"	60"	-	Custom Len.	
$115.66	$119.75	$127.91	$136.06	$152.39	-	See Web	

Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4944				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	36
6"	12"	24"	36"	60"	-	Custom Len.	
$117.63	$119.17	$122.19	$125.24	$131.31	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4960				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	37
6"	12"	24"	36"	60"	-	Custom Len.	
$148.17	$151.85	$159.17	$166.50	$181.17	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4930				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		38
6"	12"	24"	36"	60"	-	Custom Len.	
$111.33	$111.74	$112.54	$113.34	$114.94	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4889				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	39
6"	12"	24"	36"	60"	-	Custom Len.	
$115.22	$118.83	$126.04	$133.27	$147.73	-	See Web	

BMA JACK TO SMA MALE

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4908				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	40
6"	12"	24"	36"	60"	-	Custom Len.	
$119.09	$123.08	$131.02	$138.97	$154.87	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4856				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	41
6"	12"	24"	36"	60"	-	Custom Len.	
$108.15	$112.25	$120.39	$136.71	$144.88	-	See Web	

Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4941				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	42
6"	12"	24"	36"	60"	-	Custom Len.	
$111.11	$112.62	$115.64	$118.70	$124.78	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4956				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	43
6"	12"	24"	36"	60"	-	Custom Len.	
$142.32	$145.98	$153.31	$160.64	$175.33	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4926				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		44
6"	12"	24"	36"	60"	-	Custom Len.	
$106.27	$106.69	$107.50	$106.81	$108.39	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4883				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	45
6"	12"	24"	36"	60"	-	Custom Len.	
$107.70	$111.31	$118.53	$125.75	$140.21	-	See Web	

BMA JACK TO SMA MALE RIGHT ANGLE

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4911				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	46
6"	12"	24"	36"	60"	-	Custom Len.	
$121.97	$125.95	$133.91	$141.84	$157.73	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4859				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	47
6"	12"	24"	36"	60"	-	Custom Len.	
$110.21	$114.29	$122.46	$130.61	$146.92	-	See Web	

Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4943				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	48
6"	12"	24"	36"	60"	-	Custom Len.	
$127.08	$128.61	$131.64	$134.67	$140.76	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3C4958				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	49
6"	12"	24"	36"	60"	-	Custom Len.	
$153.06	$156.73	$164.05	$171.38	$186.05	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4928				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		50
6"	12"	24"	36"	60"	-	Custom Len.	
$115.60	$116.03	$116.80	$117.61	$119.21	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4886				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	51
6"	12"	24"	36"	60"	-	Custom Len.	
$109.75	$113.36	$120.58	$127.82	$142.29	-	See Web	

BMA JACK TO SMP FEMALE

Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4868				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	52
6"	12"	24"	36"	60"	-	Custom Len.	
$117.47	$121.54	$129.71	$137.86	$154.17	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4895				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	53
6"	12"	24"	36"	60"	-	Custom Len.	
$117.01	$120.63	$127.85	$135.08	$149.53	-	See Web	

BMA JACK TO SMP FEMALE RIGHT ANGLE

Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4871				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	54
6"	12"	24"	36"	60"	-	Custom Len.	
$130.21	$134.29	$142.45	$150.61	$166.93	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4898				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	55
6"	12"	24"	36"	60"	-	Custom Len.	
$129.75	$133.37	$140.58	$147.82	$162.28	-	See Web	

BMA JACK TO TNC MALE

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4917				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	56
6"	12"	24"	36"	60"	-	Custom Len.	
$123.99	$127.98	$135.93	$143.87	$159.77	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4865				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	57
6"	12"	24"	36"	60"	-	Custom Len.	
$112.25	$116.33	$124.48	$132.64	$148.96	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE3C4962				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	58
6"	12"	24"	36"	60"	-	Custom Len.	
$143.22	$146.89	$154.22	$161.55	$176.22	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4892				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	59
6"	12"	24"	36"	60"	-	Custom Len.	
$111.78	$115.39	$122.61	$129.85	$144.31	-	See Web	

BMA JACK BULKHEAD TO BMA JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4846				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	60
6"	12"	24"	36"	60"	-	Custom Len.	
$119.64	$123.72	$131.87	$140.04	$156.35	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4874				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	61
6"	12"	24"	36"	60"	-	Custom Len.	
$119.18	$122.79	$130.01	$137.24	$151.69	-	See Web	

BMA JACK 2 HOLE FLANGE TO BMA JACK 2 HOLE FLANGE

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4900				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	62
6"	12"	24"	36"	60"	-	Custom Len.	
$106.86	$110.83	$118.77	$126.73	$142.62	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4845				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	63
6"	12"	24"	36"	60"	-	Custom Len.	
$132.10	$136.19	$144.34	$152.50	$168.82	-	See Web	

Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4937				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	64
6"	12"	24"	36"	60"	-	Custom Len.	
$108.87	$110.39	$113.43	$116.46	$122.54	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4922				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		65
6"	12"	24"	36"	60"	-	Custom Len.	
$104.01	$104.42	$105.24	$106.05	$107.67	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4873				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	66
6"	12"	24"	36"	60"	-	Custom Len.	
$131.64	$135.25	$142.47	$149.70	$164.16	-	See Web	

BMA JACK 2 HOLE FLANGE TO BNC MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4919				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	67
6"	12"	24"	36"	60"	-	Custom Len.	
$92.18	$96.21	$104.27	$110.76	$126.68	-	See Web	

BMA JACK 2 HOLE FLANGE TO N MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4913				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	68
6"	12"	24"	36"	60"	-	Custom Len.	
$84.03	$88.07	$96.12	$104.18	$118.62	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4861				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	69
6"	12"	24"	36"	60"	-	Custom Len.	
$96.88	$101.03	$107.77	$115.93	$132.26	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4888				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	70
6"	12"	24"	36"	60"	-	Custom Len.	
$96.42	$100.09	$107.40	$113.14	$127.60	-	See Web	

BMA JACK 2 HOLE FLANGE TO SMA MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4907				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	71
6"	12"	24"	36"	60"	-	Custom Len.	
$75.57	$79.61	$87.67	$95.73	$110.30	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4855				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	72
6"	12"	24"	36"	60"	-	Custom Len.	
$89.27	$93.40	$101.68	$108.41	$124.75	-	See Web	

Semi-Rigid Cable Assemblies

RG402/U Coax, 50 Ohm

Part No. PE3W06981				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.1 dB/100ft	450 W	73
12"	24"	36"	48"	60"	50CM	Custom Len.	
$100.70	$107.54	$115.78	$124.00	$132.25	$106.05	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3C4882				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	74
6"	12"	24"	36"	60"	-	Custom Len.	
$88.80	$92.47	$99.83	$107.12	$120.09	-	See Web	

BMA JACK 2 HOLE FLANGE TO SMA MALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4910				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	75
6"	12"	24"	36"	60"	-	Custom Len.	
$78.49	$82.54	$90.58	$98.65	$113.16	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4858				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	76
6"	12"	24"	36"	60"	-	Custom Len.	
$91.35	$95.49	$103.76	$110.48	$126.79	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4885				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	77
6"	12"	24"	36"	60"	-	Custom Len.	
$90.88	$94.55	$101.87	$107.69	$122.15	-	See Web	

BMA JACK 2 HOLE FLANGE TO SMP FEMALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4867				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	78
6"	12"	24"	36"	60"	-	Custom Len.	
$98.71	$102.84	$109.57	$117.74	$134.05	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4894				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	79
6"	12"	24"	36"	60"	-	Custom Len.	
$98.23	$101.90	$107.71	$114.94	$129.39	-	See Web	

BMA JACK 2 HOLE FLANGE TO SMP FEMALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

Continued on Next Page

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4870				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	80
6"	12"	24"	36"	60"	-	Custom Len.	
$110.07	$114.16	$122.32	$130.48	$146.79	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4897				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	81
6"	12"	24"	36"	60"	-	Custom Len.	
$109.63	$113.24	$120.45	$127.68	$142.14	-	See Web	

BMA JACK 2 HOLE FLANGE TO TNC MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4916				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	82
6"	12"	24"	36"	60"	-	Custom Len.	
$80.55	$84.59	$92.64	$100.70	$115.21	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4864				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	83
6"	12"	24"	36"	60"	-	Custom Len.	
$93.40	$97.55	$105.82	$112.50	$128.82	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4891				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	84
6"	12"	24"	36"	60"	-	Custom Len.	
$92.94	$96.61	$103.93	$109.72	$124.18	-	See Web	

BMA JACK RIGHT ANGLE 2 HOLE FLANGE TO BMA JACK RIGHT ANGLE 2 HOLE FLANGE

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C4902				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	85
6"	12"	24"	36"	60"	-	Custom Len.	
$169.83	$173.81	$146.55	$189.70	$205.60	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4849				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	86
6"	12"	24"	36"	60"	-	Custom Len.	
$157.88	$161.96	$170.12	$178.26	$194.60	-	See Web	

Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE3C4952				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	87
6"	12"	24"	36"	60"	-	Custom Len.	
$139.65	$143.32	$150.67	$158.00	$172.66	-	See Web	

Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C4876				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	88
6"	12"	24"	36"	60"	-	Custom Len.	
$157.42	$161.04	$168.24	$175.49	$189.95	-	See Web	

BNC MALE TO BNC MALE

Standard Flexible Cable Assemblies

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0001				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			89
12"	18"	24"	30"	36"	48"	Custom Len.	
$152.60	$141.69	$144.65	$147.60	$150.55	$156.47	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0029				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			90
12"	18"	24"	30"	36"	48"	Custom Len.	
$143.40	$148.68	$153.97	$159.25	$164.56	$175.12	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0057				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			91
12"	18"	24"	30"	36"	48"	Custom Len.	
$140.34	$144.11	$147.87	$151.63	$155.39	$162.92	See Web	

M17/113-RG316-27478 Coax, 50 Ohm

Part No. PE3M0085				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.			92
6"	8"	12"	16"	18"	24"	Custom Len.	
$199.55	$199.91	$200.65	$201.35	$201.72	$202.81	See Web	

M17/119-RG174-0XDS2 Coax, 50 Ohm

Part No. PE3M0100				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.			93
6"	8"	12"	16"	18"	24"	Custom Len.	
$198.89	$199.02	$199.31	$199.59	$199.72	$200.16	See Web	

M17/28-RG058-0XDS2 Coax, 50 Ohm

Part No. PE3M0115				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			94
12"	18"	24"	30"	36"	48"	Custom Len.	
$140.24	$140.88	$141.53	$142.18	$142.83	$144.13	See Web	

BNC MALE TO N MALE

Standard Flexible Cable Assemblies

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0002				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			95
12"	18"	24"	30"	36"	48"	Custom Len.	
$166.93	$154.71	$157.67	$160.62	$163.95	$169.50	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0030				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			96
12"	18"	24"	30"	36"	48"	Custom Len.	
$156.42	$161.70	$167.00	$172.28	$177.57	$188.15	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0058				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			97
12"	18"	24"	30"	36"	48"	Custom Len.	
$153.36	$157.12	$160.89	$164.65	$168.41	$175.94	See Web	

BNC MALE TO N FEMALE

Standard Flexible Cable Assemblies

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0003				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			98
12"	18"	24"	30"	36"	48"	Custom Len.	
$162.14	$165.10	$168.05	$171.00	$173.96	$179.88	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0031				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			99
-	-	-	-	-	100CM	Custom Len.	
-	-	-	-	-	$190.93	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0059				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			1
12"	18"	24"	30"	36"	48"	Custom Len.	
$163.75	$167.52	$171.28	$175.04	$178.80	$186.33	See Web	

BNC MALE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0004				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			2
12"	18"	24"	30"	36"	48"	Custom Len.	
$166.32	$169.25	$172.22	$175.17	$178.14	$184.05	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0032				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			3
12"	18"	24"	30"	36"	48"	Custom Len.	
$170.97	$176.25	$181.56	$186.84	$192.12	$202.71	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0060				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			4
12"	18"	24"	30"	36"	48"	Custom Len.	
$167.91	$171.68	$175.44	$179.20	$182.96	$190.49	See Web	

BNC MALE TO SMA MALE

Standard Flexible Cable Assemblies

M17/128-RG400-27478 Coax, 50 Ohm

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

Part No. PE3M0061				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			5
12"	18"	24"	30"	36"	48"	Custom Len.	
$189.49	$193.25	$197.02	$200.78	$204.54	$212.07	See Web	

M17/113-RG316-27478 Coax, 50 Ohm

Part No. PE3M0086				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.			6
6"	8"	12"	16"	18"	24"	Custom Len.	
$193.65	$194.02	$194.74	$195.46	$195.84	$196.91	See Web	

M17/119-RG174-0XDS2 Coax, 50 Ohm

Part No. PE3M0101				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.			7
6"	8"	12"	16"	18"	24"	Custom Len.	
$192.99	$193.13	$193.42	$193.69	$193.83	$194.26	See Web	

M17/28-RG058-0XDS2 Coax, 50 Ohm

Part No. PE3M0116				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			8
12"	18"	24"	30"	36"	48"	Custom Len.	
$245.29	$245.92	$246.58	$247.22	$247.87	$249.17	See Web	

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0005				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			9
12"	18"	24"	30"	36"	48"	Custom Len.	
$187.87	$190.83	$193.79	$196.74	$199.70	$205.62	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0033				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			10
12"	18"	24"	30"	36"	48"	Custom Len.	
$192.55	$197.83	$203.12	$208.40	$213.70	$224.27	See Web	

BNC MALE TO SMA MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0006				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			11
12"	18"	24"	30"	36"	48"	Custom Len.	
$227.00	$229.95	$232.91	$235.87	$238.83	$244.74	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0034				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			12
12"	18"	24"	30"	36"	48"	Custom Len.	
$231.66	$236.95	$242.25	$247.52	$252.81	$263.40	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0062				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			13
12"	18"	24"	30"	36"	48"	Custom Len.	
$251.48	$232.36	$236.15	$239.90	$243.67	$251.20	See Web	

M17/113-RG316-27478 Coax, 50 Ohm

Part No. PE3M0087				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.			14
6"	8"	12"	16"	18"	24"	Custom Len.	
$210.85	$211.21	$211.94	$212.65	$213.02	$214.11	See Web	

M17/119-RG174-0XDS2 Coax, 50 Ohm

Part No. PE3M0102				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.			15
6"	8"	12"	16"	18"	24"	Custom Len.	
$210.18	$210.32	$231.67	$210.89	$211.03	$211.48	See Web	

M17/28-RG058-0XDS2 Coax, 50 Ohm

Part No. PE3M0117				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			16
12"	18"	24"	30"	36"	48"	Custom Len.	
$179.51	$180.16	$180.81	$181.45	$182.10	$183.40	See Web	

BNC MALE TO SMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

M17/113-RG316-27478 Coax, 50 Ohm

Part No. PE3M0088				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.			17
6"	8"	12"	16"	18"	24"	Custom Len.	
$200.83	$201.19	$201.92	$202.64	$203.02	$204.09	See Web	

M17/119-RG174-0XDS2 Coax, 50 Ohm

Part No. PE3M0103				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.			18
-	-	-	-	-	-	Custom Len.	
-	-	-	-	-	-	See Web	

BNC MALE TO TNC MALE

Standard Flexible Cable Assemblies

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0007				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			19
12"	18"	24"	30"	36"	48"	Custom Len.	
$170.04	$157.53	$160.67	$163.45	$166.41	$172.33	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0035				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			20
12"	18"	24"	30"	36"	48"	Custom Len.	
$159.24	$164.54	$169.82	$175.10	$180.41	$190.98	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0063				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			21
12"	18"	24"	30"	36"	48"	Custom Len.	
$156.20	$159.96	$163.72	$167.49	$171.25	$178.77	See Web	

M17/113-RG316-27478 Coax, 50 Ohm

Part No. PE3M0089				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.			22
6"	8"	12"	16"	18"	24"	Custom Len.	
$201.88	$202.23	$202.96	$203.68	$204.04	$205.13	See Web	

M17/119-RG174-0XDS2 Coax, 50 Ohm

Part No. PE3M0104				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.			23
6"	8"	12"	16"	18"	24"	Custom Len.	
$201.22	$201.39	$201.63	$201.91	$202.06	$202.48	See Web	

M17/28-RG058-0XDS2 Coax, 50 Ohm

Part No. PE3M0118				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			24
12"	18"	24"	30"	36"	48"	Custom Len.	
$211.03	$211.67	$212.32	$212.96	$213.62	$214.91	See Web	

BNC MALE TO BNC MALE

Flexible Cable Assemblies

PE-P195 Coax, 50 Ohm

Part No. PE34035				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	25
12"	24"	36"	48"	60"	-	Custom Len.	
$27.85	$37.74	$48.37	$59.06	$69.79	-	See Web	

LMR-195 Coax, 50 Ohm

Part No. PE3C0054				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		26
12"	24"	36"	48"	60"	-	Custom Len.	
$27.38	$27.44	$28.25	$29.10	$29.90	-	See Web	

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE36066				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	27
12"	24"	36"	48"	60"	-	Custom Len.	
$31.33	$32.20	$33.08	$33.99	$34.87	-	See Web	

PE-C200 Coax, 50 Ohm

Part No. PE35256				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10.8 dB/100ft	170 W	28
12"	24"	36"	48"	60"	-	Custom Len.	
$51.15	$53.85	$55.56	$62.67	$67.29	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE36219				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	29
12"	24"	36"	48"	60"	-	Custom Len.	
$58.71	$65.83	$67.07	$63.58	$69.68	-	See Web	

PE-C300 Coax, 50 Ohm

Part No. PE35729				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	6.3 dB/100ft	350 W	30
12"	24"	36"	48"	60"	-	Custom Len.	
$57.05	$60.16	$63.28	$66.39	$75.16	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE35874				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	31
12"	24"	36"	48"	60"	-	Custom Len.	
$92.01	$93.46	$97.36	$102.65	$107.92	-	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3W01041				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.			32
12"	24"	36"	48"	60"	50CM	Custom Len.	
$57.61	$58.63	$59.67	$60.71	$61.75	$58.27	See Web	

LMR-400-DB Coax, 50 Ohm

Part No. PE3C6663				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.			33
12"	24"	36"	48"	60"	50CM	Custom Len.	
$57.99	$59.40	$60.11	$61.51	$62.91	$58.20	See Web	
Part No. PE3W01357				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.15 dB/100ft		34
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.52	$65.66	$67.12	$68.58	$70.04	$65.13	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-SF200LL Coax, 50 Ohm

Part No. PE3TC1100				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.185" dia.			35
24"	36"	48"	72"	100CM	200CM	Custom Len.	
$75.22	$87.58	$99.96	$123.00	$91.07	$129.85	See Web	

LMR-200-UF Coax, 50 Ohm

Part No. PE3C2220				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.							36
12"	24"	36"	48"	60"	50CM	Custom Len.	
$50.50	$52.91	$54.81	$57.20	$59.59	$52.04	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34173				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	37
6"	12"	18"	24"	36"	48"	Custom Len.	
$95.84	$99.81	$103.68	$107.65	$113.91	$121.64	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34166				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	38
6"	12"	18"	24"	36"	48"	Custom Len.	
$139.87	$147.99	$156.07	$164.20	$180.41	$196.60	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE3462				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	39
6"	12"	18"	24"	36"	48"	Custom Len.	
$95.34	$99.65	$104.08	$107.03	$107.33	$125.05	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3776				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	40
6"	12"	18"	24"	36"	48"	Custom Len.	
$94.12	$101.64	$99.98	$105.87	$124.83	$127.58	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3807				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	41
12"	24"	36"	48"	60"	72"	Custom Len.	
$84.67	$87.79	$96.49	$94.01	$97.14	$106.96	See Web	

RG8X Coax, 50 Ohm

Part No. PE3264				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13.5 dB/100ft	60 W	42
12"	24"	36"	48"	60"	-	Custom Len.	
$71.75	$81.37	$85.25	$81.81	$93.32	-	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3067					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.195" dia.	20 dB/100ft	44 W	43
12"	18"	24"	30"	36"	48"	Custom Len.		
$34.63	$35.03	$35.44	$37.37	$36.25	$37.06	See Web		

RG58-P Coax, 50 Ohm

Part No. PE3999				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.159" dia.	17.3 dB/100ft	632 W	44
12"	24"	36"	48"	60"	-	Custom Len.	
$52.54	$57.56	$70.68	$68.54	$74.04	-	See Web	

RG141A/U Coax, 50 Ohm

Part No. PE35148				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W	45
12"	24"	36"	48"	60"	-	Custom Len.	
$51.77	$58.89	$66.47	$74.49	$82.25	-	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3495				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.		650 W	46
12"	24"	36"	48"	60"	72"	Custom Len.	
$34.99	$41.74	$48.50	$55.13	$61.93	$68.75	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C2295				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	47
12"	24"	36"	48"	60"	72"	Custom Len.	
$33.62	$34.26	$34.90	$35.57	$36.24	$36.88	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE33130				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	48
12"	24"	36"	48"	60"	-	Custom Len.	
$71.67	$72.84	$74.01	$75.24	$76.43	-	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3C2034				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	49
12"	24"	36"	48"	60"	72"	Custom Len.	
$39.89	$42.66	$45.43	$48.36	$51.16	$53.99	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3749				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	50
12"	24"	36"	48"	60"	72"	Custom Len.	
$84.99	$86.83	$92.32	$90.49	$92.30	$94.14	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3906				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	51
12"	24"	36"	48"	60"	72"	Custom Len.	
$84.19	$99.48	$106.54	$115.47	$114.79	$122.74	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3087				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	52
6"	8"	10"	12"	24"	36"	Custom Len.	
Call	Call	Call	$33.29	$36.51	$39.72	See Web	

RG303/U Coax, 50 Ohm

Part No. PE3W00393				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.17" dia.	14 dB/100ft	650 W	53
12"	24"	36"	48"	60"	50CM	Custom Len.	
$38.71	$46.35	$53.98	$61.04	$68.61	$43.59	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C2416				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	54
12"	24"	36"	48"	60"	72"	Custom Len.	
$38.24	$41.70	$45.17	$48.84	$52.37	$55.40	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3582				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	55
12"	24"	36"	48"	60"	72"	Custom Len.	
$46.59	$54.29	$62.43	$71.03	$79.32	$87.60	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3CA1097				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.			56
12"	24"	36"	48"	60"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

LMR-400-DB Coax, 50 Ohm

Part No. PE3C6665				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.			57
12"	50CM	24"	36"	100CM	48"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE34177				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	58
6"	12"	18"	24"	36"	48"	Custom Len.	
$107.50	$107.50	$113.04	$118.59	$129.70	$140.78	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE34168				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	59
6"	12"	18"	24"	36"	48"	Custom Len.	
$96.77	$101.59	$106.46	$109.74	$119.31	$128.80	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34164				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	60
6"	12"	18"	24"	36"	48"	Custom Len.	
$82.38	$92.64	$92.41	$97.43	$107.45	$115.86	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34162				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	61
6"	12"	18"	24"	36"	48"	Custom Len.	
$82.00	$86.53	$91.16	$95.76	$104.95	$112.60	See Web	

RG401/U Coax, 50 Ohm

Part No. PE34170				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	62
6"	12"	18"	24"	36"	48"	Custom Len.	
$143.31	$154.90	$166.42	$177.92	$201.02	$245.54	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3445				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	63
6"	12"	18"	24"	36"	48"	Custom Len.	
$90.26	$95.68	$94.28	$98.28	$111.31	$112.77	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3678				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	64
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.98	$84.68	$93.84	$92.01	$99.29	$106.61	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34175				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	65
6"	12"	18"	24"	36"	48"	Custom Len.	
$141.29	$150.85	$160.36	$169.92	$188.99	$208.05	See Web	

Standard Flexible Cable Assemblies

RG55B/U Coax, 53 Ohm

Part No. PE3583				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	66
12"	24"	36"	48"	60"	72"	Custom Len.	
$35.68	$38.55	$41.44	$44.47	$47.40	$50.33	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

RG59B/U Coax, 75 Ohm

Part No. PE3075				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	67
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	74 W	
12"	18"	24"	30"	36"	48"	Custom Len.	
$29.61	$31.07	$30.67	$31.21	$31.72	$32.80	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE3C3349				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	68
1 piece price shown. See web or call for volume pricing.				0.1" dia.	29.15 dB/100ft	240 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$41.46	$41.02	$43.64	$46.25	$48.88	$55.41	See Web	

RG302/U Coax, 75 Ohm

Part No. PE33123				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	69
1 piece price shown. See web or call for volume pricing.				0.206" dia.	13 dB/100ft	650 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$34.13	$40.64	$47.14	$53.65	$59.62	-	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE3081				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	70
1 piece price shown. See web or call for volume pricing.				0.239" dia.	8.7 dB/100ft	77 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$35.71	$40.28	$41.99	$43.80	$45.55	$47.29	See Web	

RG180B/U Coax, 95 Ohm

Part No. PE33574				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	71
1 piece price shown. See web or call for volume pricing.				0.145" dia.		250 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$48.28	$53.09	$53.57	$62.39	$61.86	-	See Web	

BNC MALE TO BNC MALE RIGHT ANGLE

Flexible Cable Assemblies

RG55B/U Coax, 53 Ohm

Part No. PE3C6845				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	72
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$34.55	$37.60	$39.14	$42.20	$45.26	$34.96	See Web	

Low Loss Flexible Cable Assemblies

PE-C240 Coax, 50 Ohm

Part No. PE38997				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	73
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$60.46	$58.10	$60.02	$63.06	$66.15	-	See Web	

LMR-195 Coax, 50 Ohm

Part No. PE3W01992				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	74
1 piece price shown. See web or call for volume pricing.				0.195" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$47.77	$48.56	$49.38	$50.19	$50.98	$48.28	See Web	

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE35580				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	75
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$94.89	$103.18	$109.92	$118.10	$126.26	-	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3327				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	76
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$90.44	$93.40	$96.44	$99.46	$102.43	$105.48	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3020				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	77
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.46	$57.34	$58.25	$59.18	$60.10	$61.00	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3082				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	78
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.22	$60.91	$67.59	$71.05	$77.34	$83.65	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3404				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	79
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.75	$60.39	$58.41	$61.69	$62.35	$59.85	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3C3377				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	80
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$71.81	$74.57	$77.30	$73.81	$76.25	$85.79	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3355				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	81
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$94.59	$102.24	$98.24	$100.09	$101.90	$103.73	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3325				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	82
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$98.31	$100.87	$107.45	$115.47	$123.45	$131.48	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3689				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	83
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$50.48	$53.94	$56.88	$60.51	$60.85	$64.04	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C3391				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	84
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.47	$67.76	$70.95	$74.13	$82.48	$85.96	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3358				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	85
1 piece price shown. See web or call for volume pricing.				0.114" dia.	26.1 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.02	$63.02	$65.95	$68.93	$71.93	$74.93	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3116				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	86
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.27	$80.39	$88.51	$97.14	$98.81	$112.13	See Web	

Standard Semi-Rigid Cable Assemblies

RG402/U Coax, 50 Ohm

Part No. PE39108				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	87
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$89.10	$96.49	$103.90	$109.81	$117.08	-	See Web	

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE3508				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	88
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.87	$49.99	$55.67	$51.99	$52.98	$59.19	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE3C3375				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	89
1 piece price shown. See web or call for volume pricing.				0.1" dia.	29.15 dB/100ft	240 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.78	$69.37	$79.08	$74.59	$77.17	$79.77	See Web	

BNC MALE TO 7/16 DIN FEMALE

Standard Flexible Cable Assemblies

LMR-400-UF Coax, 50 Ohm

Part No. PE3W10097				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	90
1 piece price shown. See web or call for volume pricing.				0.405" dia.	5 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$130.20	$132.14	$134.08	$136.02	$137.95	$129.50	See Web	

BNC MALE TO BNC FEMALE

Flexible Cable Assemblies

RG179B/U Coax, 75 Ohm

Part No. PE3C3741				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	91
1 piece price shown. See web or call for volume pricing.				0.1" dia.		240 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$42.37	$45.36	$46.85	$49.84	$52.83	$42.80	See Web	

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38344				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	92
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$31.39	$32.19	$32.99	$33.77	$34.57	-	See Web	

PE-SF200LL Coax, 50 Ohm

Part No. PE3TC1101				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	93
1 piece price shown. See web or call for volume pricing.				0.185" dia.			
24"	36"	48"	72"	100CM	200CM	Custom Len.	
$75.22	$87.58	$99.96	$123.00	$91.07	$129.85	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3360				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	94
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$98.80	$101.86	$104.88	$107.85	$109.35	$120.25	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

RG58C/U Coax, 50 Ohm

Part No. PE3047				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	95
12"	24"	36"	48"	60"	72"	Custom Len.	
$42.82	$43.71	$44.63	$45.58	$46.49	$47.41	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3777				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	96
12"	24"	36"	48"	60"	72"	Custom Len.	
$41.03	$47.39	$53.75	$59.57	$65.86	$72.17	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3325				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	97
12"	24"	36"	48"	60"	-	Custom Len.	
$46.18	$46.81	$44.69	$48.15	$48.79	-	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3C3453				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	98
12"	24"	36"	48"	60"	72"	Custom Len.	
$45.53	$47.85	$50.16	$52.39	$54.20	$56.43	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3949				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	99
12"	24"	36"	48"	60"	72"	Custom Len.	
$96.39	$98.13	$99.80	$101.54	$103.24	$104.97	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3371				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	1
12"	24"	36"	48"	60"	72"	Custom Len.	
$101.18	$107.77	$115.80	$123.79	$131.79	$139.80	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3606				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft		2
12"	24"	36"	48"	60"	72"	Custom Len.	
$38.93	$38.58	$45.83	$49.48	$48.25	$51.46	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C3344				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		3
12"	24"	36"	48"	60"	72"	Custom Len.	
$48.52	$52.00	$54.94	$58.58	$58.92	$65.59	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3627				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	4
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.44	$58.08	$65.73	$73.41	$81.06	$96.89	See Web	

RG55B/U Coax, 53 Ohm

Part No. PE3375				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	5
12"	24"	36"	48"	60"	72"	Custom Len.	
$36.93	$39.41	$41.90	$44.39	$46.89	$49.37	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3792				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	6
12"	24"	36"	48"	60"	72"	Custom Len.	
$31.97	$33.04	$34.11	$38.06	$36.24	$37.29	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE3368				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	7
12"	24"	36"	48"	60"	72"	Custom Len.	
$30.07	$31.54	$33.01	$34.46	$35.94	$37.39	See Web	

BNC MALE TO BNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38804				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	8
12"	24"	36"	48"	60"	-	Custom Len.	
$36.39	$40.17	$37.96	$38.74	$39.55	-	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3440				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	9
12"	24"	36"	48"	60"	72"	Custom Len.	
$103.22	$106.27	$107.77	$110.70	$113.70	$116.63	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3649				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	10
12"	24"	36"	48"	60"	72"	Custom Len.	
$49.37	$50.26	$51.17	$52.13	$53.04	$53.97	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3436				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	11
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.00	$56.29	$62.59	$68.90	$75.21	$81.50	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3397				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	12
12"	24"	36"	48"	60"	72"	Custom Len.	
$52.36	$53.00	$53.65	$49.94	$50.43	$50.90	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3C3399				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	13
12"	24"	36"	48"	60"	72"	Custom Len.	
$46.69	$49.00	$51.31	$53.55	$55.34	$57.58	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3450				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	14
12"	24"	36"	48"	60"	72"	Custom Len.	
$102.12	$103.90	$105.76	$107.59	$107.94	$109.74	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3427				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	15
12"	24"	36"	48"	60"	72"	Custom Len.	
$105.59	$112.15	$120.16	$128.15	$136.17	$144.15	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3557				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	16
12"	24"	36"	48"	60"	72"	Custom Len.	
$48.17	$51.39	$54.09	$62.02	$65.51	$63.66	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C3446				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	17
12"	24"	36"	48"	60"	72"	Custom Len.	
$48.01	$51.47	$54.45	$56.75	$59.93	$63.09	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3423				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	18
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.54	$71.67	$79.78	$88.40	$96.69	$97.15	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3103				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	19
12"	24"	36"	48"	60"	72"	Custom Len.	
$46.11	$47.18	$48.24	$49.31	$50.37	$56.07	See Web	

BNC MALE TO FAKRA PLUG

Flexible Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C7715				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	20
12"	24"	36"	48"	60"	50CM	Custom Len.	
$30.00	$30.62	$31.24	$31.87	$32.49	$29.77	See Web	

BNC MALE TO MCX JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C6788				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		21
12"	24"	36"	48"	60"	50CM	Custom Len.	
$44.44	$45.22	$45.60	$46.37	$47.15	$44.55	See Web	

BNC MALE TO MHV MALE

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3W00032				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.		44 W	22
12"	24"	36"	48"	60"	50CM	Custom Len.	
$49.16	$51.00	$51.97	$52.91	$53.87	$50.66	See Web	

BNC MALE TO N MALE

Flexible Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

LMR-240 Coax, 50 Ohm

Part No. PE3W05881				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		23
12"	24"	36"	48"	60"	50CM	Custom Len.	
$42.19	$43.15	$44.13	$45.12	$46.09	$42.81	See Web	

Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE3061				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		24
12"	24"	36"	48"	60"	72"	Custom Len.	
$49.44	$55.67	$62.35	$69.42	$70.56	$76.86	See Web	
Part No. PE3W06862				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			25
12"	24"	36"	48"	60"	50CM	Custom Len.	
$43.76	$50.30	$56.33	$62.81	$69.31	$47.94	See Web	

BNC MALE TO N MALE RIGHT ANGLE

Flexible Cable Assemblies

LMR-240 Coax, 50 Ohm

Part No. PE3C2275				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		26
12"	50CM	24"	36"	100CM	48"	Custom Len.	
$82.60	$83.23	$83.58	$84.56	$84.83	$85.54	See Web	

BNC MALE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Flexible Cable Assemblies

LMR-200 Coax, 50 Ohm

Part No. PE3W07094				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10.5 dB/100ft		27
12"	18"	24"	36"	48"	60"	Custom Len.	
$52.87	$51.27	$51.65	$52.42	$53.19	$53.95	See Web	

BNC MALE TO SHV PLUG

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3W00148				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.		44 W	28
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.72	$66.58	$67.44	$68.29	$69.16	$66.27	See Web	

BNC MALE TO SMA MALE

Low Loss Flexible Cable Assemblies

PE-C240 Coax, 50 Ohm

Part No. PE3W07719				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	7.98 dB/100ft	250 W	29
12"	24"	36"	48"	60"	50CM	Custom Len.	
$42.91	$44.31	$45.03	$46.44	$47.85	$43.10	See Web	

Standard Flexible Cable Assemblies

RG188A/U Coax, 50 Ohm

Part No. PE3W03670				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	30
12"	24"	36"	48"	60"	50CM	Custom Len.	
$49.57	$52.53	$54.98	$57.91	$60.85	$51.45	See Web	

BNC MALE TO SSMC PLUG

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4430				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		31
6"	12"	18"	24"	36"	48"	Custom Len.	
$51.03	$51.43	$47.17	$52.28	$48.40	$54.01	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4450				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	32
6"	12"	18"	24"	36"	48"	Custom Len.	
$77.44	$89.74	$85.74	$89.87	$98.13	$106.41	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4397				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	33
6"	12"	18"	24"	36"	48"	Custom Len.	
$75.45	$83.56	$76.48	$77.00	$85.90	$87.13	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4413				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	34
6"	12"	18"	24"	36"	48"	Custom Len.	
$57.56	$62.66	$60.65	$62.17	$69.51	$68.34	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4475				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	35
6"	12"	18"	24"	36"	48"	Custom Len.	
$60.86	$62.41	$58.18	$59.62	$62.49	$72.14	See Web	

BNC MALE TO SSMC PLUG RIGHT ANGLE

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4431				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		36
6"	12"	18"	24"	36"	48"	Custom Len.	
$46.83	$47.26	$43.37	$43.76	$44.59	$45.40	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4487				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	37
6"	12"	18"	24"	36"	48"	Custom Len.	
$74.05	$78.18	$82.32	$86.46	$94.73	$103.00	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4466				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	38
6"	12"	18"	24"	36"	48"	Custom Len.	
$66.20	$70.72	$67.25	$67.73	$68.77	$69.79	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4414				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	39
6"	12"	18"	24"	36"	48"	Custom Len.	
$54.29	$60.87	$56.88	$58.40	$61.49	$64.56	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4476				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	40
6"	12"	18"	24"	36"	48"	Custom Len.	
$59.16	$60.83	$56.86	$58.40	$61.50	$71.34	See Web	

BNC MALE TO SSMC JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4488				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	41
6"	12"	18"	24"	36"	48"	Custom Len.	
$69.95	$74.09	$78.23	$82.35	$90.63	$98.90	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4398				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	42
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.08	$71.60	$72.12	$72.62	$73.64	$74.68	See Web	

BNC MALE TO UHF FEMALE

Standard Flexible Cable Assemblies

RG55B/U Coax, 53 Ohm

Part No. PE3C8015				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	43
12"	24"	36"	48"	60"	50CM	Custom Len.	
$38.31	$41.42	$44.54	$47.66	$50.78	$37.18	See Web	

BNC MALE RIGHT ANGLE TO BNC MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

Continued on Next Page

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-C100-LSZH Coax, 50 Ohm — 44

Part No. PE39185				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
$61.65	$62.40	$63.18	$63.91	$64.70	-	See Web

Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm — 45

Part No. PE38249				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.101" dia.		
12"	24"	36"	48"	60"	-	Custom Len.
$73.86	$81.06	$88.25	$95.46	$102.65	-	See Web

RG8A/U Coax, 50 Ohm — 46

Part No. PE3378				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W
12"	24"	36"	48"	60"	72"	Custom Len.
$107.59	$109.09	$112.02	$115.00	$117.93	$120.94	See Web

RG58C/U Coax, 50 Ohm — 47

Part No. PE3025				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	72"	Custom Len.
$77.27	$78.15	$79.06	$80.00	$80.91	$81.81	See Web

RG142B/U Coax, 50 Ohm — 48

Part No. PE3044				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft	
12"	24"	36"	48"	60"	72"	Custom Len.
$79.13	$85.81	$87.25	$93.55	$99.86	$106.15	See Web

RG174A/U Coax, 50 Ohm — 49

Part No. PE3373				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W
12"	24"	36"	48"	60"	72"	Custom Len.
$91.62	$85.32	$85.80	$86.29	$86.76	$87.23	See Web

RG188A/U Coax, 50 Ohm — 50

Part No. PE3351				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$86.85	$89.29	$91.73	$94.17	$96.61	$107.77	See Web

RG188-DS Coax, 50 Ohm — 51

Part No. PE3381				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$81.66	$85.28	$88.92	$92.54	$96.10	$99.73	See Web

RG213/U Coax, 50 Ohm — 52

Part No. PE3384				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W
12"	24"	36"	48"	60"	72"	Custom Len.
$106.41	$106.75	$108.57	$110.38	$112.15	$113.97	See Web

RG214/U Coax, 50 Ohm — 53

Part No. PE3370				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W
12"	24"	36"	48"	60"	72"	Custom Len.
$111.11	$119.10	$127.11	$135.13	$143.11	$151.12	See Web

RG223/U Coax, 50 Ohm — 54

Part No. PE3816				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W
12"	24"	36"	48"	60"	72"	Custom Len.
$71.51	$74.70	$77.88	$81.08	$84.27	$94.67	See Web

RG316/U Coax, 50 Ohm — 55

Part No. PE3842				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$94.86	$98.30	$94.20	$97.36	$100.53	$103.71	See Web

RG316-DS Coax, 50 Ohm — 56

Part No. PE3389				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$83.73	$87.16	$90.58	$87.12	$97.72	$93.51	See Web

RG400/U Coax, 50 Ohm — 57

Part No. PE3458				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W
12"	24"	36"	48"	60"	72"	Custom Len.
$83.48	$91.15	$98.79	$106.46	$112.54	$120.11	See Web

PE-P195 Coax, 50 Ohm — 58

Part No. PE37640				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W
12"	24"	36"	48"	60"	-	Custom Len.
$74.06	$83.78	$93.51	$103.25	$111.41	-	See Web

RG55B/U Coax, 53 Ohm — 59

Part No. PE38506				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W
12"	24"	36"	48"	60"	-	Custom Len.
$62.27	$64.49	$66.81	$69.06	$71.28	-	See Web

RG59B/U Coax, 75 Ohm — 60

Part No. PE3935				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$71.36	$72.35	$73.35	$74.34	$75.32	$76.32	See Web

RG179B/U Coax, 75 Ohm — 61

Part No. PE3366				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W
12"	24"	36"	48"	60"	72"	Custom Len.
$80.67	$83.29	$85.86	$88.52	$91.10	$93.73	See Web

BNC MALE RIGHT ANGLE TO BNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm — 62

Part No. PE33189				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	-	Custom Len.
$68.94	$69.84	$70.73	$68.74	$72.59	-	See Web

RG400/U Coax, 50 Ohm — 63

Part No. PE3C3314				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$78.21	$83.09	$90.97	$98.87	$106.75	$80.25	See Web

BNC MALE RIGHT ANGLE TO SMA FEMALE

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm — 64

Part No. PE3W04854				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$59.96	$63.55	$67.15	$70.77	$74.37	$62.26	See Web

BNC MALE RIGHT ANGLE TO TNC MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

LMR-240-UF Coax, 50 Ohm — 65

Part No. PE3W07480				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft	
12"	18"	24"	36"	48"	60"	Custom Len.
$75.11	$73.01	$73.73	$75.16	$76.59	$78.01	See Web

BNC FEMALE TO BNC MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm — 66

Part No. PE3W06649				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$93.17	$93.78	$94.40	$95.01	$95.63	$93.55	See Web

BNC FEMALE TO BNC FEMALE

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm — 67

Part No. PE36345				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W
12"	24"	36"	48"	60"	-	Custom Len.
$114.63	$117.41	$120.28	$123.08	$125.94	-	See Web

RG58C/U Coax, 50 Ohm — 68

Part No. PE3052				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	72"	Custom Len.
$43.41	$44.23	$49.56	$50.50	$46.68	$52.34	See Web

RG142B/U Coax, 50 Ohm — 69

Part No. PE3088				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft	
12"	24"	36"	48"	60"	72"	Custom Len.
$41.60	$47.71	$53.91	$64.12	$65.61	$71.71	See Web

RG174A/U Coax, 50 Ohm — 70

Part No. PE3604				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W
12"	24"	36"	48"	60"	72"	Custom Len.
$56.27	$56.91	$57.55	$58.23	$56.01	$59.51	See Web

RG178B/U Coax, 50 Ohm — 71

Part No. PE36455				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W
12"	24"	36"	48"	60"	-	Custom Len.
$80.70	$75.80	$83.02	$84.27	$78.96	-	See Web

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

RG188A/U Coax, 50 Ohm

Part No. PE3094				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	72
12"	24"	36"	48"	60"	72"	Custom Len.	
$57.18	$65.64	$62.06	$64.50	$66.95	$69.38	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3953				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	73
12"	24"	36"	48"	60"	72"	Custom Len.	
$127.76	$135.77	$143.77	$151.78	$159.77	$167.79	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3364				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	74
12"	24"	36"	48"	60"	72"	Custom Len.	
$38.67	$41.92	$45.12	$53.11	$51.65	$54.35	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3505				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	75
12"	24"	36"	48"	60"	72"	Custom Len.	
$58.18	$61.35	$69.71	$73.34	$70.90	$74.06	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C6575				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	130 W	76
12"	24"	36"	48"	60"	50CM	Custom Len.	
$50.88	$54.48	$57.56	$61.13	$64.70	$53.19	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3675				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	77
12"	24"	36"	48"	60"	72"	Custom Len.	
$26.31	$27.31	$27.53	$28.50	$29.45	$30.42	See Web	

BNC FEMALE TO SMA MALE

Flexible Cable Assemblies

RG316-DS Coax, 50 Ohm

Part No. PE3C6914				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	130 W	78
12"	24"	36"	48"	60"	50CM	Custom Len.	
$42.00	$45.60	$47.41	$51.02	$54.12	$42.50	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W06305				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	79
12"	18"	24"	36"	48"	60"	Custom Len.	
$51.08	$49.47	$49.76	$50.36	$50.96	$51.56	See Web	

BNC FEMALE BULKHEAD TO SMA MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W03377				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.		121.5 W	80
12"	24"	36"	48"	60"	50CM	Custom Len.	
$83.65	$93.49	$103.34	$111.61	$121.32	$89.96	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3W01634				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	80 W	81
12"	24"	36"	48"	60"	50CM	Custom Len.	
$37.32	$38.27	$39.23	$40.19	$41.14	$37.93	See Web	

C MALE TO C MALE

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE33316				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	82
12"	24"	36"	48"	60"	72"	Custom Len.	
$106.59	$116.32	$112.75	$115.81	$118.89	$121.96	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3457				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	83
12"	24"	36"	48"	60"	72"	Custom Len.	
$100.47	$101.28	$108.76	$102.87	$103.68	$104.51	See Web	

RG141A/U Coax, 50 Ohm

Part No. PE34440				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W	84
12"	24"	36"	48"	60"	72"	Custom Len.	
$89.85	$96.77	$103.62	$108.94	$115.75	$122.49	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3518				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	85
12"	24"	36"	48"	60"	72"	Custom Len.	
$82.01	$88.29	$94.60	$100.90	$107.21	$111.94	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3522				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	86
12"	24"	36"	48"	60"	72"	Custom Len.	
$106.83	$107.15	$108.94	$110.75	$112.55	$114.36	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3605				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	87
12"	24"	36"	48"	60"	72"	Custom Len.	
$98.67	$106.71	$120.01	$121.13	$129.06	$146.13	See Web	

RG217/U Coax, 50 Ohm

Part No. PE34437				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.	5.8 dB/100ft	260 W	88
12"	24"	36"	48"	60"	72"	Custom Len.	
$165.57	$170.35	$175.12	$179.89	$196.38	$189.45	See Web	

RG218/U Coax, 50 Ohm

Part No. PE34442				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.87" dia.	3.8 dB/100ft	560 W	89
12"	24"	36"	48"	60"	72"	Custom Len.	
$248.98	$261.09	$273.13	$285.24	$297.31	$309.43	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3343				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	90
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.87	$82.05	$85.24	$88.42	$91.61	$94.81	See Web	

RG225/U Coax, 50 Ohm

Part No. PE33098				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.	7.5 dB/100ft	1,700 W	91
12"	24"	36"	48"	60"	72"	Custom Len.	
$119.10	$154.44	$189.77	$225.09	$260.44	$295.78	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3120				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	92
12"	24"	36"	48"	60"	72"	Custom Len.	
$106.73	$130.91	$148.70	$157.04	$185.67	$203.80	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3545				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	93
12"	24"	36"	48"	60"	72"	Custom Len.	
$84.09	$91.82	$99.53	$107.26	$113.37	$120.99	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE33662				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	94
12"	24"	36"	48"	60"	72"	Custom Len.	
$107.00	$107.98	$107.45	$108.42	$109.41	$110.38	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE34435				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	95
12"	24"	36"	48"	60"	72"	Custom Len.	
$107.45	$107.40	$108.83	$110.26	$111.70	$113.12	See Web	

FAKRA PLUG TO FAKRA PLUG

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38747A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		96
12"	24"	36"	48"	60"	-	Custom Len.	
$24.53	$25.36	$26.17	$26.93	$27.74	-	See Web	

Part No. PE38747C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		97
12"	24"	36"	48"	60"	-	Custom Len.	
$24.94	$27.89	$28.55	$30.67	$32.86	-	See Web	

Part No. PE38747D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		98
12"	24"	36"	48"	60"	-	Custom Len.	
$25.90	$27.40	$29.66	$31.87	$34.13	-	See Web	

Part No. PE38747H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		99
12"	24"	36"	48"	60"	-	Custom Len.	
$24.53	$25.36	$26.17	$26.93	$27.74	-	See Web	

Part No. PE38747I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		1
12"	24"	36"	48"	60"	-	Custom Len.	
$25.90	$27.40	$29.66	$31.87	$34.13	-	See Web	

Part No. PE38747K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		2
12"	24"	36"	48"	60"	-	Custom Len.	
$25.90	$27.40	$29.66	$31.87	$34.13	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

Part No. PE38747Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		3
12"	24"	36"	48"	60"	-	Custom Len.	
$29.94	$29.06	$30.42	$34.44	$35.95	-	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE38751A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	4
12"	24"	36"	48"	60"	-	Custom Len.	
$29.54	$30.14	$30.72	$31.28	$31.87	-	See Web	

Part No. PE38751C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	5
12"	24"	36"	48"	60"	-	Custom Len.	
$32.50	$30.14	$30.72	$31.28	$31.87	-	See Web	

Part No. PE38751D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	6
12"	24"	36"	48"	60"	-	Custom Len.	
$29.54	$30.14	$30.72	$31.28	$31.87	-	See Web	

Part No. PE38751H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	7
12"	24"	36"	48"	60"	-	Custom Len.	
$29.54	$30.14	$30.72	$31.28	$31.87	-	See Web	

Part No. PE38751I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	8
12"	24"	36"	48"	60"	-	Custom Len.	
$29.54	$30.14	$30.72	$31.28	$31.87	-	See Web	

Part No. PE38751K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	9
12"	24"	36"	48"	60"	-	Custom Len.	
$29.54	$30.14	$30.72	$31.28	$31.87	-	See Web	

Part No. PE38751Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	10
12"	24"	36"	48"	60"	-	Custom Len.	
$35.75	$32.99	$33.47	$33.96	$38.37	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE38755A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	11
12"	24"	36"	48"	60"	-	Custom Len.	
$32.20	$35.33	$38.53	$41.72	$44.91	-	See Web	

Part No. PE38755C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	12
12"	24"	36"	48"	60"	-	Custom Len.	
$34.09	$34.01	$37.09	$40.16	$43.23	-	See Web	

Part No. PE38755D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	13
12"	24"	36"	48"	60"	-	Custom Len.	
$32.20	$35.33	$38.53	$41.72	$44.91	-	See Web	

Part No. PE38755H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	14
12"	24"	36"	48"	60"	-	Custom Len.	
$32.20	$35.33	$38.53	$41.72	$44.91	-	See Web	

Part No. PE38755I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	15
12"	24"	36"	48"	60"	-	Custom Len.	
$32.20	$35.33	$38.53	$41.72	$44.91	-	See Web	

Part No. PE38755K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	16
12"	24"	36"	48"	60"	-	Custom Len.	
$32.20	$35.33	$38.53	$41.72	$44.91	-	See Web	

Part No. PE38755Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	17
12"	24"	36"	48"	60"	-	Custom Len.	
$32.20	$35.33	$38.53	$46.02	$44.91	-	See Web	

FAKRA PLUG TO FAKRA JACK

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38748A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		18
12"	24"	36"	48"	60"	-	Custom Len.	
$27.72	$29.06	$30.42	$31.87	$36.50	-	See Web	

Part No. PE38748C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		19
12"	24"	36"	48"	60"	-	Custom Len.	
$30.49	$29.06	$33.45	$31.87	$36.50	-	See Web	

Part No. PE38748D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		20
12"	24"	36"	48"	60"	-	Custom Len.	
$27.72	$29.06	$30.42	$31.87	$36.50	-	See Web	

Part No. PE38748H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		21
12"	24"	36"	48"	60"	-	Custom Len.	
$27.72	$29.06	$30.42	$31.87	$34.13	-	See Web	

Part No. PE38748I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		22
12"	24"	36"	48"	60"	-	Custom Len.	
$25.90	$27.40	$29.66	$31.87	$34.13	-	See Web	

Part No. PE38748K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		23
12"	24"	36"	48"	60"	-	Custom Len.	
$27.72	$29.06	$32.89	$31.87	$35.95	-	See Web	

Part No. PE38748Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		24
12"	24"	36"	48"	60"	-	Custom Len.	
$29.40	$30.88	$32.35	$33.93	$35.42	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C2779				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.			25
12"	24"	36"	48"	60"	50CM	Custom Len.	
$26.88	$27.74	$27.82	$28.64	$29.46	$27.43	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE38752A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	26
12"	24"	36"	48"	60"	-	Custom Len.	
$32.50	$32.99	$33.47	$33.96	$34.43	-	See Web	

Part No. PE38752C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	27
12"	24"	36"	48"	60"	-	Custom Len.	
$32.50	$32.99	$33.47	$33.96	$38.37	-	See Web	

Part No. PE38752D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	28
12"	24"	36"	48"	60"	-	Custom Len.	
$32.50	$32.99	$33.47	$37.06	$34.43	-	See Web	

Part No. PE38752H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	29
12"	24"	36"	48"	60"	-	Custom Len.	
$32.50	$32.99	$33.47	$33.96	$37.72	-	See Web	

Part No. PE38752I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	30
12"	24"	36"	48"	60"	-	Custom Len.	
$32.50	$32.99	$33.47	$33.96	$38.37	-	See Web	

Part No. PE38752K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	31
12"	24"	36"	48"	60"	-	Custom Len.	
$31.91	$35.10	$32.87	$36.42	$33.84	-	See Web	

Part No. PE38752Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	32
12"	24"	36"	48"	60"	-	Custom Len.	
$34.46	$35.10	$35.75	$36.42	$37.08	-	See Web	

FAKRA PLUG TO FAKRA JACK RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38749A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		33
12"	24"	36"	48"	60"	-	Custom Len.	
$27.34	$28.79	$31.06	$33.27	$35.53	-	See Web	

Part No. PE38749B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		34
12"	24"	36"	48"	60"	-	Custom Len.	
$27.57	$25.79	$26.56	$27.31	$27.34	-	See Web	

Part No. PE38749C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		35
12"	24"	36"	48"	60"	-	Custom Len.	
$27.34	$28.79	$31.06	$33.76	$35.53	-	See Web	

Part No. PE38749D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		36
12"	24"	36"	48"	60"	-	Custom Len.	
$27.88	$29.23	$30.55	$31.89	$33.22	-	See Web	

Part No. PE38749H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		37
12"	24"	36"	48"	60"	-	Custom Len.	
$25.06	$25.79	$26.56	$27.31	$27.34	-	See Web	

Part No. PE38749I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		38
12"	24"	36"	48"	60"	-	Custom Len.	
$25.06	$25.79	$26.56	$27.31	$27.34	-	See Web	

Part No. PE38749K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		39
12"	24"	36"	48"	60"	-	Custom Len.	
$27.88	$29.23	$30.55	$31.89	$33.22	-	See Web	

Part No. PE38749Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		40
12"	24"	36"	48"	60"	-	Custom Len.	
$29.28	$30.61	$31.94	$33.29	$35.53	-	See Web	

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

See Our Website For Current Pricing & Real-Time Stock Availability!

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE38753A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	41
12"	24"	36"	48"	60"	-	Custom Len.	
$36.86	$37.39	$37.98	$38.58	$39.13	-	See Web	

Part No. PE38753C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	42
12"	24"	36"	48"	60"	-	Custom Len.	
$39.82	$40.29	$40.78	$41.26	$45.61	-	See Web	

Part No. PE38753D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	43
12"	24"	36"	48"	60"	-	Custom Len.	
$36.86	$37.39	$37.98	$38.58	$39.13	-	See Web	

Part No. PE38753H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	44
12"	24"	36"	48"	60"	-	Custom Len.	
$40.54	$41.03	$41.52	$42.00	$42.48	-	See Web	

Part No. PE38753I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	45
12"	24"	36"	48"	60"	-	Custom Len.	
$36.86	$37.39	$37.98	$38.58	$39.13	-	See Web	

Part No. PE38753K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	46
12"	24"	36"	48"	60"	-	Custom Len.	
$36.86	$37.39	$37.98	$38.58	$39.13	-	See Web	

Part No. PE38753Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	47
12"	24"	36"	48"	60"	-	Custom Len.	
$43.79	$44.43	$41.52	$42.00	$42.48	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE38757A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	48
12"	24"	36"	48"	60"	-	Custom Len.	
$39.44	$42.66	$45.86	$48.98	$52.17	-	See Web	

Part No. PE38757C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	49
12"	24"	36"	48"	60"	-	Custom Len.	
$39.44	$42.66	$45.86	$48.98	$52.17	-	See Web	

Part No. PE38757D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	50
12"	24"	36"	48"	60"	-	Custom Len.	
$39.44	$42.66	$45.86	$48.98	$52.17	-	See Web	

Part No. PE38757H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	51
12"	24"	36"	48"	60"	-	Custom Len.	
$39.44	$42.66	$45.86	$48.98	$52.17	-	See Web	

Part No. PE38757I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	52
12"	24"	36"	48"	60"	-	Custom Len.	
$39.44	$42.66	$45.86	$48.98	$52.17	-	See Web	

Part No. PE38757K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	53
12"	24"	36"	48"	60"	-	Custom Len.	
$39.44	$42.66	$45.86	$48.98	$52.17	-	See Web	

FAKRA PLUG TO SMA MALE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C6275				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	54
12"	-	-	-	-	-	Custom Len.	
Call	-	-	-	-	-	See Web	

FAKRA JACK TO FAKRA JACK

Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38746A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft	40 W	55
12"	24"	36"	48"	60"	-	Custom Len.	
$30.49	$31.96	$30.42	$31.87	$34.13	-	See Web	

Part No. PE38746Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft	40 W	56
12"	24"	36"	48"	60"	-	Custom Len.	
$26.96	$27.70	$29.18	$30.73	$32.25	-	See Web	

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38746B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		57
12"	24"	36"	48"	60"	-	Custom Len.	
$29.94	$31.41	$30.42	$31.87	$35.95	-	See Web	

Part No. PE38746C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		58
12"	24"	36"	48"	60"	-	Custom Len.	
$30.49	$31.96	$30.42	$34.99	$36.50	-	See Web	

Part No. PE38746D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		59
12"	24"	36"	48"	60"	-	Custom Len.	
$27.72	$29.06	$32.89	$34.44	$34.13	-	See Web	

Part No. PE38746H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		60
12"	24"	36"	48"	60"	-	Custom Len.	
$24.53	$25.36	$26.17	$26.93	$27.74	-	See Web	

Part No. PE38746I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		61
12"	24"	36"	48"	60"	-	Custom Len.	
$27.72	$29.06	$33.45	$31.87	$36.50	-	See Web	

Part No. PE38746K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		62
12"	24"	36"	48"	60"	-	Custom Len.	
$27.72	$29.06	$30.42	$34.99	$34.13	-	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE38750A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	63
12"	24"	36"	48"	60"	-	Custom Len.	
$32.50	$32.99	$37.03	$33.96	$34.43	-	See Web	

Part No. PE38750B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	64
12"	24"	36"	48"	60"	-	Custom Len.	
$29.54	$30.14	$33.18	$31.28	$31.87	-	See Web	

Part No. PE38750C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	65
12"	24"	36"	48"	60"	-	Custom Len.	
$32.50	$32.99	$35.72	$33.96	$37.06	-	See Web	

Part No. PE38750D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	66
12"	24"	36"	48"	60"	-	Custom Len.	
$32.50	$32.99	$36.39	$33.96	$37.72	-	See Web	

Part No. PE38750H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	67
12"	24"	36"	48"	60"	-	Custom Len.	
$31.91	$35.10	$32.87	$36.42	$33.84	-	See Web	

Part No. PE38750I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	68
12"	24"	36"	48"	60"	-	Custom Len.	
$29.54	$30.14	$30.72	$31.28	$31.87	-	See Web	

Part No. PE38750K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	69
12"	24"	36"	48"	60"	-	Custom Len.	
$32.50	$35.74	$33.47	$33.96	$34.43	-	See Web	

Part No. PE38750Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	70
12"	24"	36"	48"	60"	-	Custom Len.	
$32.57	$33.21	$33.86	$34.55	$35.19	-	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE3W02209				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	71
12"	24"	36"	48"	60"	50CM	Custom Len.	
$33.82	$37.62	$41.41	$45.21	$49.00	$36.26	See Web	

RG316/U Coax, 50 Ohm

Part No. PE38754A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	72
12"	24"	36"	48"	60"	-	Custom Len.	
$35.42	$38.62	$41.83	$45.04	$48.25	-	See Web	

Part No. PE38754B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	73
12"	24"	36"	48"	60"	-	Custom Len.	
$32.20	$35.33	$38.53	$41.72	$44.91	-	See Web	

Part No. PE38754C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	74
12"	24"	36"	48"	60"	-	Custom Len.	
$34.13	$37.59	$41.07	$41.72	$44.91	-	See Web	

Part No. PE38754D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	75
12"	24"	36"	48"	60"	-	Custom Len.	
$35.42	$38.90	$38.53	$41.72	$44.91	-	See Web	

Part No. PE38754H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	76
12"	24"	36"	48"	60"	-	Custom Len.	
$32.20	$35.33	$41.07	$41.72	$44.91	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

Part No. PE38754I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	77
12"	24"	36"	48"	60"	-	Custom Len.	
$32.20	$35.33	$38.53	$41.72	$44.91	-	See Web	

Part No. PE38754K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	78
12"	24"	36"	48"	60"	-	Custom Len.	
$32.20	$35.33	$38.53	$41.72	$44.91	-	See Web	

Part No. PE38754Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		79
12"	24"	36"	48"	60"	-	Custom Len.	
$35.82	$39.29	$42.77	$46.43	$49.97	-	See Web	

FAKRA JACK TO FAKRA JACK RIGHT ANGLE

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W02943				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		80
12"	24"	36"	48"	60"	50CM	Custom Len.	
$27.11	$27.96	$28.02	$28.84	$29.65	$27.66	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C7911				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	81
12"	24"	36"	48"	60"	50CM	Custom Len.	
$35.81	$36.43	$37.05	$37.68	$38.30	$35.58	See Web	

FAKRA JACK TO MCX PLUG

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C7585				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		82
12"	24"	36"	48"	60"	50CM	Custom Len.	
$40.47	$44.11	$47.75	$51.39	$54.52	$42.80	See Web	

FAKRA JACK TO SMA FEMALE

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE39351Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		83
12"	24"	36"	48"	60"	-	Custom Len.	
$62.23	$59.75	$62.95	$66.12	$69.30	-	See Web	

FAKRA JACK TO REVERSE POLARITY TNC MALE

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W03361				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		84
12"	24"	36"	48"	60"	50CM	Custom Len.	
$44.78	$45.58	$46.40	$47.20	$48.00	$45.29	See Web	

FAKRA JACK RIGHT ANGLE TO FAKRA PLUG

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE38757Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		85
12"	24"	36"	48"	60"	-	Custom Len.	
$47.74	$46.61	$49.81	$53.01	$55.71	-	See Web	

FME PLUG TO BNC MALE

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE35959				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	86
12"	24"	36"	48"	60"	72"	Custom Len.	
$44.88	$45.71	$46.52	$47.33	$48.16	$48.98	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE35962				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	87
12"	24"	36"	48"	60"	72"	Custom Len.	
$38.58	$44.72	$50.91	$56.52	$62.67	$68.74	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3420				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	88
12"	24"	36"	48"	60"	72"	Custom Len.	
$40.33	$40.80	$41.31	$41.74	$42.21	$42.71	See Web	

FME PLUG TO FME PLUG

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38719				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	89
12"	24"	36"	48"	60"	-	Custom Len.	
$39.44	$40.25	$40.99	$41.72	$42.51	-	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE35953				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	90
12"	24"	36"	48"	60"	72"	Custom Len.	
$46.19	$46.99	$47.80	$48.65	$49.45	$50.23	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE35955				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	91
12"	24"	36"	48"	60"	72"	Custom Len.	
$42.85	$48.98	$54.66	$60.73	$66.81	$72.95	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE35957				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	92
12"	24"	36"	48"	60"	72"	Custom Len.	
$44.46	$44.91	$45.39	$45.92	$46.38	$46.92	See Web	

FME PLUG BULKHEAD TO UMCX PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

PE-113mm Coax, 50 Ohm

Part No. PE38858				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.044" dia.			93
6"	12"	18"	-	-	-	Custom Len.	
$34.44	Call	Call	-	-	-	See Web	

FME JACK TO BNC MALE

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE34862				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	94
12"	24"	36"	48"	60"	72"	Custom Len.	
$36.73	$37.53	$38.39	$39.19	$39.98	$40.80	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE34864				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	95
12"	24"	36"	48"	60"	72"	Custom Len.	
$35.27	$41.39	$47.53	$53.72	$59.30	$65.42	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3409				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	96
12"	24"	36"	48"	60"	72"	Custom Len.	
$40.48	$40.92	$41.44	$41.88	$42.40	$42.84	See Web	

FME JACK TO FME JACK

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE34856				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	97
12"	24"	36"	48"	60"	72"	Custom Len.	
$41.96	$42.78	$43.58	$44.41	$45.23	$46.04	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE34858				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	98
12"	24"	36"	48"	60"	72"	Custom Len.	
$36.12	$42.24	$48.46	$54.08	$60.21	$66.27	See Web	

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

See Our Website For Current Pricing & Real-Time Stock Availability!

RG174A/U Coax, 50 Ohm

Part No. PE34860				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	99
12"	24"	36"	48"	60"	72"	Custom Len.	
$49.19	$45.19	$45.73	$46.19	$46.71	$47.18	See Web	

GR874 SEXLESS TO BNC MALE

Standard Flexible Cable Assemblies

RG214/U Coax, 50 Ohm

Part No. PE3145				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	1
12"	24"	36"	48"	60"	72"	Custom Len.	
$150.47	$158.48	$166.48	$174.48	$182.47	$190.49	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3182				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	2
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.20	$57.45	$60.61	$63.85	$67.06	$70.24	See Web	

GR874 SEXLESS TO GR874 SEXLESS

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3211				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	3
12"	24"	36"	48"	60"	72"	Custom Len.	
$81.53	$82.32	$83.12	$83.89	$84.68	$85.54	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3200				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		4
12"	24"	36"	48"	60"	72"	Custom Len.	
$80.19	$86.26	$92.41	$98.49	$104.56	$109.17	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3158				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	5
12"	24"	36"	48"	60"	72"	Custom Len.	
$222.62	$230.63	$238.64	$246.65	$254.65	$262.64	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3190				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	6
12"	24"	36"	48"	60"	72"	Custom Len.	
$81.94	$85.13	$88.31	$91.48	$94.68	$97.87	See Web	

HN MALE TO 7/16 DIN MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

RG217/U Coax, 50 Ohm

Part No. PE3W03391				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.	5.8 dB/100ft	260 W	7
12"	24"	36"	48"	60"	50CM	Custom Len.	
$281.60	$286.91	$292.23	$297.53	$302.86	$285.01	See Web	

HN MALE TO HN MALE

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE33304				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	8
12"	24"	36"	48"	60"	72"	Custom Len.	
$121.10	$124.17	$135.02	$138.55	$133.39	$136.44	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3852				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	9
12"	24"	36"	48"	60"	72"	Custom Len.	
$95.78	$96.60	$97.41	$98.21	$99.03	$99.84	See Web	

RG141A/U Coax, 50 Ohm

Part No. PE34434				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W	10
12"	24"	36"	48"	60"	72"	Custom Len.	
$103.04	$108.42	$115.21	$121.96	$128.74	$135.50	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3083				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		11
12"	24"	36"	48"	60"	72"	Custom Len.	
$99.65	$105.95	$117.33	$124.31	$123.12	$137.74	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3038				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	9 dB/100ft	190 W	12
12"	24"	36"	48"	60"	72"	Custom Len.	
$127.02	$128.96	$130.89	$132.94	$134.92	$136.90	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3095				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	13
12"	24"	36"	48"	60"	72"	Custom Len.	
$136.54	$136.75	$144.70	$162.33	$170.93	$179.54	See Web	

RG217/U Coax, 50 Ohm

Part No. PE33370				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.	5.8 dB/100ft	260 W	14
12"	24"	36"	48"	60"	72"	Custom Len.	
$136.64	$141.77	$146.87	$152.29	$157.51	$162.73	See Web	

RG218/U Coax, 50 Ohm

Part No. PE33583				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.87" dia.	3.8 dB/100ft	560 W	15
12"	24"	36"	48"	60"	72"	Custom Len.	
$303.06	$315.15	$327.26	$339.30	$351.40	$363.50	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3357				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	16
12"	24"	36"	48"	60"	72"	Custom Len.	
$96.58	$105.79	$107.70	$106.13	$114.71	$110.95	See Web	

RG225/U Coax, 50 Ohm

Part No. PE33778				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	17
12"	24"	36"	48"	60"	72"	Custom Len.	
$157.76	$194.20	$230.62	$267.05	$303.48	$339.91	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3340				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	18
12"	24"	36"	48"	60"	72"	Custom Len.	
$141.27	$150.04	$176.84	$195.66	$213.78	$231.93	See Web	

RG400/U Coax, 50 Ohm

Part No. PE33938				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	19
12"	24"	36"	48"	60"	72"	Custom Len.	
$113.21	$114.36	$121.93	$129.48	$137.04	$144.60	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE34436				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	20
12"	24"	36"	48"	60"	72"	Custom Len.	
$120.22	$121.19	$122.17	$123.14	$124.12	$125.09	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE34438				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	21
12"	24"	36"	48"	60"	72"	Custom Len.	
$120.67	$122.10	$123.53	$124.97	$126.40	$127.84	See Web	

HN MALE RIGHT ANGLE TO HN FEMALE

Standard Flexible Cable Assemblies

RG213/U Coax, 50 Ohm

Part No. PE3W05081				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.		190 W	22
12"	24"	36"	48"	60"	50CM	Custom Len.	
$147.09	$149.10	$151.12	$153.14	$155.15	$148.38	See Web	

LC MALE TO LC MALE



Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE33541				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	23
60"	72"	84"	96"	108"	120"	Custom Len.	
$424.34	$430.40	$436.38	$442.35	$448.40	$454.41	See Web	

RG214/U Coax, 50 Ohm

Part No. PE33491				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	24
60"	72"	84"	96"	108"	120"	Custom Len.	
$385.63	$393.63	$401.65	$409.63	$417.64	$425.65	See Web	

RG217/U Coax, 50 Ohm

Part No. PE33537				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.	5.8 dB/100ft	260 W	25
60"	72"	84"	96"	108"	120"	Custom Len.	
$433.82	$438.59	$443.36	$448.13	$452.91	$457.69	See Web	

RG218/U Coax, 50 Ohm

Part No. PE3960				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.87" dia.	3.8 dB/100ft	560 W	26
60"	72"	84"	96"	108"	120"	Custom Len.	
$573.42	$552.46	$564.92	$577.38	$589.84	$602.31	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

RG225/U Coax, 50 Ohm

Part No. PE34538				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	27
60"	72"	84"	96"	108"	120"	Custom Len.	
$522.27	$557.61	$592.93	$628.27	$663.60	$698.93	See Web	

RG393/U Coax, 50 Ohm

Part No. PE33539				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	28
60"	72"	84"	96"	108"	120"	Custom Len.	
$479.83	$497.97	$484.87	$534.23	$518.40	$535.18	See Web	

LC MALE RIGHT ANGLE TO HN MALE

Standard Flexible Cable Assemblies

RG393/U Coax, 50 Ohm

Part No. PE3W00314				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.		1,700 W	29
12"	24"	36"	48"	60"	50CM	Custom Len.	
$328.05	$345.32	$362.57	$379.85	$397.12	$339.10	See Web	

MC-CARD PLUG TO MC-CARD PLUG

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36114				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	30
12"	24"	36"	48"	60"	72"	Custom Len.	
$45.86	$46.38	$46.84	$47.31	$47.86	$48.30	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36116				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	31
12"	24"	36"	48"	60"	72"	Custom Len.	
$46.45	$47.53	$48.56	$49.65	$50.73	$51.76	See Web	

RG316/U Coax, 50 Ohm

Part No. PE36118				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	32
12"	24"	36"	48"	60"	72"	Custom Len.	
$48.73	$52.04	$54.86	$58.18	$61.46	$64.77	See Web	

MC-CARD PLUG TO MC-CARD PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36120				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	33
12"	24"	36"	48"	60"	72"	Custom Len.	
$46.78	$47.26	$47.80	$48.25	$48.79	$49.25	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36122				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	34
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.35	$55.39	$56.46	$57.50	$58.56	$59.62	See Web	

RG316/U Coax, 50 Ohm

Part No. PE36124				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	35
12"	24"	36"	48"	60"	72"	Custom Len.	
$49.65	$52.98	$55.78	$59.09	$62.40	$65.69	See Web	

MC-CARD PLUG RIGHT ANGLE TO MC-CARD PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36126				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	36
12"	24"	36"	48"	60"	-	Custom Len.	
$47.71	$48.19	$48.73	$49.17	$49.65	-	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36128				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	37
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.11	$57.17	$58.24	$59.30	$60.33	$61.40	See Web	

RG316/U Coax, 50 Ohm

Part No. PE36130				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	38
12"	24"	36"	48"	60"	72"	Custom Len.	
$50.50	$53.85	$56.64	$59.94	$63.25	$66.53	See Web	

MCX PLUG TO BNC MALE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C3387				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	39
12"	50CM	24"	36"	100CM	48"	Custom Len.	
$42.94	$40.16	$40.39	$41.01	$41.17	$41.63	See Web	

MCX PLUG TO MCX PLUG

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3295				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	40
12"	24"	36"	48"	60"	72"	Custom Len.	
$51.54	$52.02	$52.52	$52.99	$53.47	$53.95	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3290				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	41
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.56	$55.50	$57.95	$60.39	$68.50	$65.26	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE3293				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	42
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.04	$62.56	$64.07	$65.57	$67.07	$68.58	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3297				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		43
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.25	$56.23	$59.40	$62.58	$70.26	$68.93	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE36799				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	44
12"	41CM	48CM	56CM	24"	36"	Custom Len.	
Call	Call	Call	Call	$53.55	$60.72	See Web	

MCX PLUG TO MCX PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3314				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	45
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.19	$54.18	$54.65	$55.13	$55.61	$56.08	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3309				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	46
12"	24"	36"	48"	60"	72"	Custom Len.	
$52.98	$54.86	$57.17	$59.55	$61.86	$64.24	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE3311				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	47
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.78	$57.23	$58.70	$60.15	$61.60	$63.06	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3316				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		48
12"	24"	36"	48"	60"	72"	Custom Len.	
$57.69	$60.86	$64.04	$67.22	$70.39	$73.56	See Web	

MCX PLUG TO SMA MALE

Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W06468				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		49
12"	24"	36"	48"	60"	50CM	Custom Len.	
$41.22	$42.02	$42.83	$43.64	$44.44	$41.73	See Web	

MCX PLUG TO TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

See Our Website For Current Pricing & Real-Time Stock Availability!

RG174A/U Coax, 50 Ohm

Part No. PE3W03310				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	50
12"	24"	36"	48"	60"	50CM	Custom Len.	
$90.50	$91.11	$91.73	$92.34	$92.96	$90.88	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3W05645				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		51
12"	24"	36"	48"	60"	50CM	Custom Len.	
$100.71	$104.31	$107.92	$109.99	$113.54	$103.03	See Web	

MCX PLUG RIGHT ANGLE TO BNC FEMALE 4 HOLE FLANGE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG316-DS Coax, 50 Ohm

Part No. PE3W01570				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	52
12"	24"	36"	48"	60"	50CM	Custom Len.	
$81.45	$84.77	$88.11	$91.44	$94.79	$83.56	See Web	

MCX PLUG RIGHT ANGLE TO MCX PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3304				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	53
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.02	$54.48	$55.00	$55.44	$55.93	$56.46	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3299				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	54
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.33	$62.77	$65.23	$67.66	$70.10	$72.54	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE3301				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	55
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.06	$56.52	$57.96	$59.43	$60.86	$62.33	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3306				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		56
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.45	$65.63	$68.80	$71.98	$75.16	$78.33	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE37099				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	57
12"	24"	36"	48"	60"	-	Custom Len.	
$62.29	$65.49	$74.15	$71.88	$75.08	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE35463				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	58
12"	24"	36"	48"	60"	-	Custom Len.	
$71.59	$79.26	$86.91	$94.57	$102.24	-	See Web	

MCX PLUG RIGHT ANGLE TO MCX JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W01300				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	59
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.88	$67.11	$67.72	$68.34	$68.95	$66.88	See Web	

MCX PLUG RIGHT ANGLE TO SMA MALE

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W07396				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	60
12"	24"	36"	48"	60"	50CM	Custom Len.	
$104.65	$112.89	$122.60	$132.31	$141.94	$109.41	See Web	
Part No. PE3W07964				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	61
12"	24"	36"	48"	60"	50CM	Custom Len.	
$50.61	$60.00	$69.85	$79.70	$89.55	$56.46	See Web	

MCX JACK TO MCX JACK

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3W00099				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	62
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.24	$76.47	$77.71	$78.96	$80.21	$76.03	See Web	

MHV MALE TO MHV MALE

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3098				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	63
12"	24"	36"	48"	60"	72"	Custom Len.	
$103.60	$111.62	$108.29	$111.37	$121.86	$125.26	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3516				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	64
12"	24"	36"	48"	60"	72"	Custom Len.	
$85.51	$86.40	$87.29	$88.24	$89.15	$90.07	See Web	

RG141A/U Coax, 50 Ohm

Part No. PE34429				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W	65
12"	24"	36"	48"	60"	72"	Custom Len.	
$94.12	$101.21	$113.34	$121.27	$128.88	$127.80	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3914				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		66
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.98	$71.26	$77.57	$82.52	$90.17	$96.12	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE34427				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	67
12"	24"	36"	48"	60"	72"	Custom Len.	
$107.82	$106.80	$111.83	$107.74	$113.13	$113.77	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34431				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	68
12"	24"	36"	48"	60"	72"	Custom Len.	
$110.30	$112.70	$115.10	$117.52	$119.92	$122.32	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3735				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	69
12"	24"	36"	48"	60"	72"	Custom Len.	
$115.80	$117.19	$132.66	$133.08	$141.02	$148.96	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3694				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	70
12"	24"	36"	48"	60"	72"	Custom Len.	
$65.55	$65.02	$68.21	$76.00	$74.59	$82.98	See Web	

RG225/U Coax, 50 Ohm

Part No. PE34423				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	71
12"	24"	36"	48"	60"	72"	Custom Len.	
$128.48	$163.80	$199.13	$234.48	$269.80	$305.13	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34433				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	72
12"	24"	36"	48"	60"	72"	Custom Len.	
$104.56	$107.85	$109.60	$112.86	$116.12	$119.37	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3577				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W	73
12"	24"	36"	48"	60"	72"	Custom Len.	
$116.67	$141.45	$150.20	$166.98	$183.74	$200.50	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34425				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	74
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.87	$81.53	$89.21	$96.86	$104.53	$118.09	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3542				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	75
12"	24"	36"	48"	60"	72"	Custom Len.	
$50.38	$55.07	$56.20	$53.58	$58.57	$59.74	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

RG62A/U Coax, 93 Ohm

Part No. PE3517				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	76
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.94	$55.14	$56.83	$54.94	$56.47	$62.08	See Web	

MHV MALE TO MHV MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE35799				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	77
12"	24"	36"	48"	60"	-	Custom Len.	
$111.46	$112.09	$112.70	$106.55	$107.03	-	See Web	

MHV MALE TO SHV PLUG

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3365				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	78
12"	24"	36"	48"	60"	72"	Custom Len.	
$105.25	$106.87	$109.93	$113.00	$116.07	$119.14	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3950				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	79
12"	24"	36"	48"	60"	72"	Custom Len.	
$97.83	$106.55	$107.44	$100.25	$107.77	$108.68	See Web	

RG141A/U Coax, 50 Ohm

Part No. PE34413				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W	80
12"	24"	36"	48"	60"	72"	Custom Len.	
$103.54	$109.11	$127.29	$135.21	$130.09	$137.11	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3085				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		81
12"	24"	36"	48"	60"	72"	Custom Len.	
$96.38	$102.70	$107.47	$113.68	$119.90	$134.34	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE34419				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	82
12"	24"	36"	48"	60"	72"	Custom Len.	
$111.33	$107.00	$112.60	$107.98	$106.93	$107.45	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34415				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	83
12"	24"	36"	48"	60"	72"	Custom Len.	
$106.88	$109.22	$111.49	$113.83	$116.12	$118.44	See Web	

RG214/U Coax, 50 Ohm

Part No. PE33516				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	84
12"	24"	36"	48"	60"	72"	Custom Len.	
$117.54	$118.83	$126.77	$134.70	$151.93	$150.60	See Web	

RG223/U Coax, 50 Ohm

Part No. PE34411				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	85
12"	24"	36"	48"	60"	72"	Custom Len.	
$79.34	$82.55	$90.94	$88.92	$92.09	$101.56	See Web	

RG225/U Coax, 50 Ohm

Part No. PE34407				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	86
12"	24"	36"	48"	60"	72"	Custom Len.	
$131.93	$167.25	$202.58	$237.92	$273.24	$308.58	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34417				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	87
12"	24"	36"	48"	60"	72"	Custom Len.	
$107.77	$111.04	$114.29	$117.55	$120.80	$124.03	See Web	

RG393/U Coax, 50 Ohm

Part No. PE33984				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	88
12"	24"	36"	48"	60"	72"	Custom Len.	
$119.51	$136.27	$153.05	$169.81	$186.57	$203.35	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34409				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	89
12"	24"	36"	48"	60"	72"	Custom Len.	
$84.57	$92.28	$100.00	$107.72	$113.83	$129.25	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3108				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	90
12"	24"	36"	48"	60"	72"	Custom Len.	
$81.32	$82.44	$77.40	$84.80	$79.50	$87.12	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE3451				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	91
12"	24"	36"	48"	60"	72"	Custom Len.	
$74.40	$75.91	$77.42	$78.92	$80.43	$81.96	See Web	

MINI SMP FEMALE TO MINI SMP FEMALE RIGHT ANGLE

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C6069				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	92
12"	24"	36"	48"	60"	50CM	Custom Len.	
$119.19	$128.91	$138.63	$148.34	$158.05	$125.42	See Web	

MINI SMP FEMALE TO SMA MALE RIGHT ANGLE

Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE3C7629				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	93
12"	24"	36"	48"	60"	50CM	Custom Len.	
$104.70	$115.91	$128.57	$141.23	$153.90	$111.35	See Web	

MINI UHF MALE TO MINI UHF MALE

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3258				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	94
12"	24"	36"	48"	60"	72"	Custom Len.	
$35.65	$36.47	$37.28	$38.10	$42.89	$39.72	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3263				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		95
12"	24"	36"	48"	60"	72"	Custom Len.	
$35.56	$39.06	$45.25	$51.38	$57.05	$63.11	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3265				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	96
12"	24"	36"	48"	60"	72"	Custom Len.	
$29.99	$33.27	$39.91	$39.72	$42.98	$46.19	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3269				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	97
12"	24"	36"	48"	60"	72"	Custom Len.	
$41.26	$49.05	$56.32	$64.03	$71.77	$79.48	See Web	

MMBX PLUG TO MMBX PLUG

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4064				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	121.5 W	98
4"	6"	8"	12"	18"	24"	Custom Len.	
$55.10	$56.48	$57.85	$66.68	$64.74	$68.89	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4031				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	99
4"	6"	8"	12"	18"	24"	Custom Len.	
$49.53	$49.60	$49.68	$49.84	$50.06	$50.30	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3985				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	1
4"	6"	8"	12"	18"	24"	Custom Len.	
$49.70	$49.87	$50.05	$50.40	$50.91	$51.43	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4014				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	58 dB/100ft	160 W	2
4"	6"	8"	12"	18"	24"	Custom Len.	
$50.40	$50.91	$51.43	$52.48	$54.03	$55.07	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4048				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	3
4"	6"	8"	12"	18"	24"	Custom Len.	
$50.42	$50.92	$51.45	$52.51	$54.06	$55.13	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

MMBX PLUG TO MMBX PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4032				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	4
4"	6"	8"	12"	18"	24"	Custom Len.	
$53.73	$53.81	$53.88	$54.04	$54.28	$54.50	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3986				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	5
4"	6"	8"	12"	18"	24"	Custom Len.	
$53.91	$54.07	$54.24	$54.10	$54.61	$55.13	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4015				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	58 dB/100ft	160 W	6
4"	6"	8"	12"	18"	24"	Custom Len.	
$54.10	$54.61	$55.13	$56.16	$57.70	$59.22	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4049				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	7
4"	6"	8"	12"	18"	24"	Custom Len.	
$54.11	$54.62	$55.15	$56.19	$57.73	$59.30	See Web	

MMBX PLUG TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4040				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	8
4"	6"	8"	12"	18"	24"	Custom Len.	
$64.52	$64.60	$64.69	$64.84	$65.06	$65.30	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3993				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	9
4"	6"	8"	12"	18"	24"	Custom Len.	
$58.36	$58.53	$58.71	$59.06	$59.57	$60.07	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4023				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	58 dB/100ft	160 W	10
4"	6"	8"	12"	18"	24"	Custom Len.	
$65.40	$65.91	$66.42	$67.45	$69.00	$70.53	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4056				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	11
4"	6"	8"	12"	18"	24"	Custom Len.	
$66.18	$66.69	$67.21	$68.24	$69.79	$71.35	See Web	

MMBX PLUG TO SMA MALE

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4068				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	121.5 W	12
4"	6"	8"	12"	18"	24"	Custom Len.	
$54.04	$50.98	$52.38	$60.12	$58.80	$62.95	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4036				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	13
4"	6"	8"	12"	18"	24"	Custom Len.	
$46.60	$46.68	$46.76	$51.61	$47.14	$52.24	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3989				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	14
4"	6"	8"	12"	18"	24"	Custom Len.	
$54.69	$54.85	$55.04	$55.38	$55.89	$56.40	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4019				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	15
4"	6"	8"	12"	18"	24"	Custom Len.	
$47.49	$47.99	$48.51	$54.50	$51.10	$57.46	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C3854				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	16
4"	6"	8"	12"	18"	24"	Custom Len.	
$42.23	$42.75	$43.28	$44.31	$45.88	$47.44	See Web	

MMBX PLUG TO SMA MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4044				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	17
4"	6"	8"	12"	18"	24"	Custom Len.	
$57.14	$57.20	$57.30	$57.45	$57.68	$57.91	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3997				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	18
4"	6"	8"	12"	18"	24"	Custom Len.	
$64.16	$64.32	$64.49	$64.84	$65.34	$65.86	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4027				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	19
4"	6"	8"	12"	18"	24"	Custom Len.	
$58.00	$58.52	$59.04	$60.06	$61.60	$63.14	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4060				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	20
4"	6"	8"	12"	18"	24"	Custom Len.	
$56.46	$56.95	$57.48	$58.52	$60.06	$61.62	See Web	

MMBX PLUG TO SMA FEMALE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4046				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	21
4"	6"	8"	12"	18"	24"	Custom Len.	
$56.31	$56.37	$56.47	$56.61	$56.85	$57.08	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3999				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	22
4"	6"	8"	12"	18"	24"	Custom Len.	
$63.93	$64.10	$64.28	$64.62	$65.13	$65.65	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4029				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	23
4"	6"	8"	12"	18"	24"	Custom Len.	
$57.17	$57.69	$58.21	$65.15	$60.77	$62.30	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4062				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	24
4"	6"	8"	12"	18"	24"	Custom Len.	
$56.45	$56.94	$57.47	$58.51	$60.05	$61.61	See Web	

MMBX PLUG TO SMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4066				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	121.5 W	25
4"	6"	8"	12"	18"	24"	Custom Len.	
$57.20	$53.88	$54.77	$63.28	$61.65	$65.81	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4034				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	26
4"	6"	8"	12"	18"	24"	Custom Len.	
$52.55	$52.62	$52.71	$57.61	$57.93	$53.33	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3922				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	27
4"	6"	8"	12"	18"	24"	Custom Len.	
$57.85	$58.01	$58.21	$58.54	$59.15	$59.57	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4017				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	58 dB/100ft	160 W	28
4"	6"	8"	12"	18"	24"	Custom Len.	
$53.43	$53.94	$54.46	$55.00	$56.53	$58.07	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4051				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	29
4"	6"	8"	12"	18"	24"	Custom Len.	
$59.63	$60.14	$60.66	$61.69	$63.25	$64.80	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

MMBX PLUG TO REVERSE POLARITY SMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4038				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	30
4"	6"	8"	12"	18"	24"	Custom Len.	
$62.68	$62.74	$62.82	$62.99	$63.21	$63.44	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3991				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	31
4"	6"	8"	12"	18"	24"	Custom Len.	
$45.99	$46.16	$46.34	$46.69	$47.20	$47.71	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4021				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	58 dB/100ft	160 W	32
4"	6"	8"	12"	18"	24"	Custom Len.	
$63.55	$64.05	$64.56	$65.60	$67.13	$68.67	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4054				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	33
4"	6"	8"	12"	18"	24"	Custom Len.	
$64.17	$64.68	$65.19	$66.23	$67.77	$69.34	See Web	

MMBX PLUG TO SSMB JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W07532				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		34
12"	24"	36"	48"	60"	50CM	Custom Len.	
$76.04	$79.63	$83.24	$86.85	$90.47	$78.34	See Web	

MMBX PLUG TO TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4042				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	35
4"	6"	8"	12"	18"	24"	Custom Len.	
$60.98	$61.05	$61.14	$61.29	$61.52	$61.76	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3995				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	36
4"	6"	8"	12"	18"	24"	Custom Len.	
$62.00	$58.67	$58.85	$62.74	$59.71	$60.23	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4025				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	37
4"	6"	8"	12"	18"	24"	Custom Len.	
$61.86	$62.36	$62.87	$70.30	$65.44	$66.99	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4058				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	38
4"	6"	8"	12"	18"	24"	Custom Len.	
$61.45	$61.95	$62.48	$63.52	$65.06	$66.63	See Web	

MMBX PLUG RIGHT ANGLE TO MMBX PLUG RIGHT ANGLE

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4065				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	121.5 W	39
4"	6"	8"	12"	18"	24"	Custom Len.	
$65.25	$66.63	$68.00	$70.77	$74.90	$79.04	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4033				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	40
4"	6"	8"	12"	18"	24"	Custom Len.	
$57.40	$57.47	$57.56	$57.71	$57.94	$58.18	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3987				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	41
4"	6"	8"	12"	18"	24"	Custom Len.	
$57.59	$57.74	$57.93	$58.27	$58.79	$59.30	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4016				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	42
4"	6"	8"	12"	18"	24"	Custom Len.	
$58.27	$58.79	$59.30	$66.36	$61.87	$63.39	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4050				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	43
4"	6"	8"	12"	18"	24"	Custom Len.	
$58.28	$58.80	$59.32	$60.34	$61.90	$63.45	See Web	

MMBX PLUG RIGHT ANGLE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4041				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	44
4"	6"	8"	12"	18"	24"	Custom Len.	
$68.70	$68.77	$68.84	$69.01	$69.23	$69.47	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3994				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	45
4"	6"	8"	12"	18"	24"	Custom Len.	
$62.53	$62.70	$62.87	$63.23	$63.74	$64.24	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4024				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	58 dB/100ft	160 W	46
4"	6"	8"	12"	18"	24"	Custom Len.	
$69.56	$70.08	$70.59	$71.62	$73.16	$74.70	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4057				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	47
4"	6"	8"	12"	18"	24"	Custom Len.	
$70.35	$70.84	$71.37	$72.41	$73.95	$75.52	See Web	

MMBX PLUG RIGHT ANGLE TO SMA MALE

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4069				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	121.5 W	48
4"	6"	8"	12"	18"	24"	Custom Len.	
$56.75	$53.46	$54.35	$62.82	$61.25	$65.39	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4037				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	49
4"	6"	8"	12"	18"	24"	Custom Len.	
$50.81	$50.88	$50.96	$54.18	$51.35	$51.58	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3990				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	50
4"	6"	8"	12"	18"	24"	Custom Len.	
$58.85	$59.02	$59.19	$59.55	$60.05	$60.57	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4020				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	51
4"	6"	8"	12"	18"	24"	Custom Len.	
$92.77	$92.90	$93.05	$98.92	$93.72	$102.35	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4053				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	52
4"	6"	8"	12"	18"	24"	Custom Len.	
$46.44	$46.96	$47.49	$53.38	$54.60	$51.66	See Web	

MMBX PLUG RIGHT ANGLE TO SMA MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4045				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	53
4"	6"	8"	12"	18"	24"	Custom Len.	
$61.31	$61.38	$61.46	$61.61	$61.85	$62.07	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3998				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	54
4"	6"	8"	12"	18"	24"	Custom Len.	
$68.30	$68.49	$68.66	$69.01	$69.51	$70.03	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

RG316/U Coax, 50 Ohm

Part No. PE3C4028				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	55
4"	6"	8"	12"	18"	24"	Custom Len.	
$62.17	$62.69	$63.20	$64.23	$65.78	$67.31	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4061				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	56
4"	6"	8"	12"	18"	24"	Custom Len.	
$60.61	$61.13	$61.64	$62.69	$64.23	$65.80	See Web	

MMBX PLUG RIGHT ANGLE TO SMA FEMALE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4047				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	57
4"	6"	8"	12"	18"	24"	Custom Len.	
$60.46	$60.55	$60.63	$60.78	$61.00	$61.25	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3W03154				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	58
4"	6"	8"	12"	18"	24"	Custom Len.	
$68.10	$68.26	$68.46	$68.79	$69.31	$69.82	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4030				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	59
4"	6"	8"	12"	18"	24"	Custom Len.	
$67.50	$68.07	$62.36	$69.73	$64.95	$66.47	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4063				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	60
4"	6"	8"	12"	18"	24"	Custom Len.	
$66.73	$61.12	$61.63	$68.94	$64.22	$65.79	See Web	

MMBX PLUG RIGHT ANGLE TO SMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4067				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	121.5 W	61
4"	6"	8"	12"	18"	24"	Custom Len.	
$59.90	$55.84	$57.21	$65.97	$64.11	$68.25	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4035				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	62
4"	6"	8"	12"	18"	24"	Custom Len.	
$56.24	$56.31	$56.38	$62.19	$62.52	$57.02	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C4807				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	63
12"	24"	36"	48"	60"	50CM	Custom Len.	
$78.47	$76.58	$77.71	$78.84	$79.97	$76.17	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4018				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	64
4"	6"	8"	12"	18"	24"	Custom Len.	
$62.72	$62.72	$62.72	$62.72	$64.30	$65.88	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4052				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	65
4"	6"	8"	12"	18"	24"	Custom Len.	
$63.80	$64.30	$64.83	$65.86	$67.41	$68.96	See Web	

MMBX PLUG RIGHT ANGLE TO REVERSE POLARITY SMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4039				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	66
4"	6"	8"	12"	18"	24"	Custom Len.	
$66.84	$66.91	$67.00	$67.14	$67.38	$67.61	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3992				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	67
4"	6"	8"	12"	18"	24"	Custom Len.	
$54.71	$50.36	$50.54	$55.46	$51.41	$51.93	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4022				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	58 dB/100ft	160 W	68
4"	6"	8"	12"	18"	24"	Custom Len.	
$67.70	$68.22	$68.74	$69.77	$71.30	$72.84	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4055				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	69
4"	6"	8"	12"	18"	24"	Custom Len.	
$68.33	$68.83	$69.36	$70.40	$71.94	$73.51	See Web	

MMBX PLUG RIGHT ANGLE TO TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C4043				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	70
4"	6"	8"	12"	18"	24"	Custom Len.	
$65.14	$65.23	$65.30	$72.00	$72.32	$65.92	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3996				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	71
4"	6"	8"	12"	18"	24"	Custom Len.	
$68.94	$62.84	$63.02	$69.70	$63.88	$64.39	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4026				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	72
4"	6"	8"	12"	18"	24"	Custom Len.	
$66.01	$66.52	$67.04	$72.16	$73.88	$71.14	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4059				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	73
4"	6"	8"	12"	18"	24"	Custom Len.	
$65.61	$66.13	$66.66	$74.45	$76.17	$70.79	See Web	

MMCX PLUG TO MMCX PLUG

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE34879				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	74
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.18	$59.90	$65.44	$60.86	$61.34	$61.82	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE34598				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	75
12"	24"	36"	48"	60"	72"	Custom Len.	
$65.04	$66.20	$61.24	$62.29	$63.34	$64.41	See Web	
Part No. PE34599				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	76
4"	-	-	-	-	-	Custom Len.	
$97.39	-	-	-	-	-	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34885				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	77
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.87	$58.24	$60.55	$62.90	$65.23	$67.61	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE34891				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	78
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.13	$55.61	$57.05	$58.51	$59.94	$61.40	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34240				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		79
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.81	$65.25	$68.80	$71.98	$75.16	$78.33	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE38679				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	80
12"	24"	36"	48"	60"	-	Custom Len.	
$56.77	$59.97	$63.16	$66.37	$69.56	-	See Web	

MMCX PLUG TO MMCX PLUG RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38231				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		81
12"	24"	36"	48"	60"	-	Custom Len.	
$53.87	$54.70	$56.01	$57.35	$58.67	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE38322				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	82
12"	24"	36"	48"	60"	-	Custom Len.	
$90.57	$93.55	$101.64	$108.23	$116.21	-	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE34881				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	83
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.86	$68.50	$63.80	$64.26	$64.74	$65.23	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE34883				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	84
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.43	$69.47	$70.53	$71.59	$72.63	$73.69	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34889				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	85
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.86	$74.09	$69.75	$72.18	$74.63	$77.06	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE34893				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	86
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.59	$64.03	$65.51	$66.95	$68.39	$69.85	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34895				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	87
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.45	$75.89	$72.22	$75.39	$78.57	$81.74	See Web	

MMCX PLUG TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE3W07591				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					36 dB/100ft	32 W	88
12"	24"	36"	48"	60"	50CM	Custom Len.	
$96.19	$105.73	$113.65	$123.07	$132.47	$102.30	See Web	

MMCX PLUG TO SMC PLUG

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3W07653				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	89
12"	24"	36"	48"	60"	50CM	Custom Len.	
$53.85	$54.59	$55.84	$57.08	$58.32	$54.15	See Web	

MMCX PLUG RIGHT ANGLE TO BNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36738				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	90
12"	24"	36"	48"	60"	-	Custom Len.	
$63.89	$64.51	$65.15	$61.72	$66.47	-	See Web	

MMCX PLUG RIGHT ANGLE TO MMCX PLUG

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W05483				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	91
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.10	$80.67	$90.52	$100.37	$108.68	$77.14	See Web	

MMCX PLUG RIGHT ANGLE TO SMA MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W07894				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		92
12"	18"	24"	36"	48"	60"	Custom Len.	
$80.19	$78.93	$80.67	$84.14	$87.61	$91.09	See Web	

MMCX PLUG RIGHT ANGLE TO SMA FEMALE

Standard Flexible Cable Assemblies

RG188-DS Coax, 50 Ohm

Part No. PE3W07068				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.118" dia.	30 dB/100ft	160 W	93
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.65	Call	Call	Call	Call	Call	See Web	

N MALE TO N MALE

Flexible Cable Assemblies

PE-C500 Coax, 50 Ohm

Part No. PE35522				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.5" dia.	3.5 dB/100ft	720 W	94
12"	24"	36"	48"	60"	-	Custom Len.	
$98.75	$103.16	$107.59	$110.46	$114.80	-	See Web	

LMR-195 Coax, 50 Ohm

Part No. PE3C0118				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		95
12"	24"	36"	48"	60"	-	Custom Len.	
$52.58	$53.40	$51.26	$54.61	$55.44	-	See Web	

Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C0124				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		96
12"	24"	36"	48"	60"	-	Custom Len.	
$159.39	$146.94	$150.32	$153.90	$157.34	-	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4137				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	97
12"	24"	36"	48"	60"	50CM	Custom Len.	
$96.43	$102.56	$107.19	$113.24	$119.30	$100.37	See Web	

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE37940				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	98
36"	48"	60"	72"	120"	-	Custom Len.	
$35.82	$36.74	$37.63	$38.50	$42.05	-	See Web	

PE-C200 Coax, 50 Ohm

Part No. PE34693				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10.8 dB/100ft	170 W	99
12"	24"	36"	48"	60"	-	Custom Len.	
$50.67	$52.44	$56.58	$61.20	$65.82	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE37941				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	1
36"	48"	60"	72"	120"	-	Custom Len.	
$54.53	$55.86	$54.13	$58.39	$68.33	-	See Web	

PE-C300 Coax, 50 Ohm

Part No. PE36634				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	6.3 dB/100ft	350 W	2
12"	24"	36"	48"	60"	-	Custom Len.	
$75.29	$74.15	$82.50	$80.37	$83.49	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE34666				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	3
12"	24"	36"	48"	60"	-	Custom Len.	
$64.48	$68.70	$70.33	$72.06	$75.79	-	See Web	
Part No. PE37942				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	4
36"	48"	60"	72"	-	-	Custom Len.	
$72.32	$74.06	$70.94	$72.39	-	-	See Web	

PE-C600 Coax, 50 Ohm

Part No. PE37943				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.7 dB/100ft	900 W	5
36"	48"	60"	72"	120"	100CM	Custom Len.	
$113.37	$116.06	$118.74	$121.43	$140.57	$120.88	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3C0039				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		6
12"	24"	36"	48"	60"	-	Custom Len.	
$45.81	$46.89	$47.95	$49.10	$50.21	-	See Web	
Part No. PE3C0053				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		7
12"	24"	36"	48"	60"	-	Custom Len.	
$59.85	$60.79	$61.73	$62.66	$63.60	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

Part No. PE3C0101				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		8
12"	24"	36"	48"	60"	-	Custom Len.	
$50.73	$51.81	$52.89	$54.04	$54.62	-	See Web	

LMR-400 Coax, 50 Ohm

Part No. PE3C0033				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		9
12"	24"	36"	48"	60"	-	Custom Len.	
$53.75	$54.77	$56.29	$57.90	$59.45	-	See Web	
Part No. PE3C0046				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		10
12"	24"	36"	48"	60"	-	Custom Len.	
$54.61	$56.13	$57.66	$59.24	$60.81	-	See Web	
Part No. PE3C0105				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		11
12"	24"	36"	48"	60"	-	Custom Len.	
$88.69	$90.20	$91.72	$93.33	$94.87	-	See Web	

LMR-600 Coax, 50 Ohm

Part No. PE3C0048				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft		12
12"	24"	36"	48"	60"	-	Custom Len.	
$154.63	$157.71	$152.02	$164.05	$158.17	-	See Web	
Part No. PE3C0062				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft		13
12"	24"	36"	48"	60"	-	Custom Len.	
$150.64	$153.72	$156.79	$160.04	$163.17	-	See Web	
Part No. PE3C0110				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft		14
12"	24"	36"	48"	60"	-	Custom Len.	
$122.85	$125.93	$122.05	$125.11	$135.39	-	See Web	
Part No. PE3C0112				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft		15
12"	24"	36"	48"	60"	-	Custom Len.	
$86.05	$84.29	$87.41	$90.52	$93.64	-	See Web	

LMR-195 Coax, 50 Ohm

Part No. PE3C0060				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		16
12"	24"	36"	48"	60"	-	Custom Len.	
$48.64	$49.47	$47.55	$48.38	$52.03	-	See Web	
Part No. PE3C0061				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		17
12"	24"	36"	48"	60"	-	Custom Len.	
$47.26	$48.08	$48.91	$47.07	$50.65	-	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE343				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		18
12"	24"	36"	48"	60"	50CM	Custom Len.	
$130.34	$147.93	$165.54	$183.15	$200.75	$141.62	See Web	
Part No. PE3C0231				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.32" dia.	7.2 dB/100ft		19
24"	36"	48"	60"	72"	120"	Custom Len.	
$360.33	$443.81	$456.25	$491.23	$512.12	$779.19	See Web	

PE-SF200LL Coax, 50 Ohm

Part No. PE3TC1102				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.185" dia.			20
24"	36"	48"	72"	100CM	200CM	Custom Len.	
$85.32	$97.70	$108.56	$124.84	$101.17	$139.83	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5255				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			21
12"	24"	36"	48"	60"	50CM	Custom Len.	
$222.74	$245.21	$267.66	$290.11	$312.56	$237.13	See Web	

LMR-600-UF Coax, 50 Ohm

Part No. PE3C7615				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.			22
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.81	$77.64	$81.46	$85.28	$89.10	$72.43	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0174				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			23
12"	18"	24"	36"	48"	60"	Custom Len.	
$401.21	$410.40	$419.59	$437.98	$456.36	$474.75	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0219				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			24
8"	12"	18"	24"	30"	36"	Custom Len.	
$369.32	$374.62	$382.61	$390.56	$398.54	$406.49	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0247				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			25
12"	18"	24"	36"	48"	60"	Custom Len.	
$453.26	$468.59	$483.94	$514.63	$545.32	$576.00	See Web	

Precision Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39465				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	26
6"	9"	12"	18"	24"	-	Custom Len.	
$58.24	$60.68	$58.24	$62.40	$72.03	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39457				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	27
6"	9"	12"	18"	24"	-	Custom Len.	
$49.60	Call	$40.60	Call	Call	-	See Web	

PE-80TEST Coax, 50 Ohm

Part No. PE3TC0103				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			28
24"	48"	72"	200CM	-	400CM	Custom Len.	
$369.28	$462.24	$555.20	Call	-	Call	See Web	

PE-90TEST Coax, 50 Ohm

Part No. PE3TC0302				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.151" dia.			29
24"	48"	72"	144"	180"	300"	Custom Len.	
$301.67	$386.18	$470.70	Call	Call	Call	See Web	

Low PIM Formable Cable Assemblies

PE-SR401FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2011				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.276" dia.			30
100CM	200CM	-	-	-	-	Custom Len.	
$119.19	$153.65	-	-	-	-	See Web	

PE-SR402FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2000				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.			31
76CM	100CM	150CM	200CM	-	-	Custom Len.	
Call	$87.88	Call	$100.95	-	-	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7842				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		32
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.21	$62.95	$66.67	$70.40	$74.13	$61.60	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6202				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	33
12"	24"	36"	48"	60"	50CM	Custom Len.	
$57.61	$63.75	$69.88	$76.00	$82.14	$61.52	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C6345				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			34
12"	24"	36"	48"	60"	50CM	Custom Len.	
$48.96	$51.26	$53.56	$55.35	$57.64	$50.43	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C6360				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			35
12"	24"	36"	48"	60"	50CM	Custom Len.	
$49.69	$52.73	$55.27	$58.28	$61.29	$51.64	See Web	

SPP-500-LLPL Coax, 50 Ohm

Part No. PE3C6370				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.5" dia.			36
12"	24"	36"	48"	60"	50CM	Custom Len.	
$52.15	$61.95	$72.25	$82.53	$92.80	$58.26	See Web	

SPO-500 Coax, 50 Ohm

Part No. PE3C6371				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.53" dia.			37
12"	24"	36"	48"	60"	50CM	Custom Len.	
$39.59	$42.70	$45.82	$48.92	$52.04	$41.59	See Web	

SPF-500 Coax, 50 Ohm

Part No. PE3C6374				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.			38
12"	24"	36"	48"	60"	50CM	Custom Len.	
$40.90	$44.02	$47.13	$50.24	$53.35	$42.90	See Web	

SPP-375-LLPL Coax, 50 Ohm

Part No. PE3C6385				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.402" dia.			39
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.53	$70.52	$78.51	$86.50	$94.50	$67.65	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE330				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	4.6 dB/100ft		40
12"	24"	36"	48"	60"	50CM	Custom Len.	
$292.87	$320.99	$349.12	$377.23	$405.34	$310.89	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34146				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	41
6"	12"	18"	24"	36"	48"	Custom Len.	
$98.80	$102.78	$106.67	$109.09	$116.81	$124.57	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34149				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	42
6"	12"	18"	24"	36"	48"	Custom Len.	
$144.12	$152.77	$152.48	$170.46	$188.17	$206.90	See Web	
Part No. PE3W00109				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						1,400 W	43
12"	24"	36"	48"	60"	50CM	Custom Len.	
$107.57	$125.96	$144.36	$162.75	$181.14	$119.36	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE3472				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	44
6"	12"	18"	24"	36"	48"	Custom Len.	
$91.68	$96.00	$100.42	$104.86	$107.13	$113.81	See Web	
Part No. PE39451				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	400 W	45
6"	9"	12"	18"	24"	-	Custom Len.	
$68.84	Call	$58.47	$62.61	$66.76	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE39443				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	46
6"	9"	12"	18"	24"	-	Custom Len.	
$61.82	Call	Call	$78.09	$70.35	-	See Web	
Part No. PE3963				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	47
6"	12"	18"	24"	36"	48"	Custom Len.	
$121.22	$121.22	$127.02	$132.82	$144.41	$156.00	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3570				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	48
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.88	$75.32	$78.70	$82.28	$85.72	$89.15	See Web	

RG8X Coax, 50 Ohm

Part No. PE33720				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13.5 dB/100ft	60 W	49
12"	24"	36"	48"	60"	-	Custom Len.	
$80.28	$79.09	$82.43	$92.15	$89.16	-	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3441				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	50
12"	24"	36"	48"	60"	72"	Custom Len.	
$52.73	$53.62	$54.03	$54.98	$55.89	$56.80	See Web	

RG141A/U Coax, 50 Ohm

Part No. PE36589				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W	51
12"	24"	36"	48"	60"	-	Custom Len.	
$66.99	$78.59	$86.18	$94.22	$101.95	-	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3455				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	52
6"	12"	18"	24"	30"	36"	Custom Len.	
$52.50	$55.26	$58.58	$61.93	$63.09	$68.62	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE36273				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	53
12"	24"	36"	48"	60"	-	Custom Len.	
$55.92	$61.01	$56.88	$62.34	$62.98	-	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE33527				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	54
12"	24"	36"	48"	60"	72"	Custom Len.	
$84.18	$85.35	$81.53	$82.58	$83.64	$84.68	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE33525				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	55
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.17	$64.61	$67.05	$69.49	$71.93	$74.37	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3496				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	56
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.37	$71.34	$73.29	$75.38	$77.38	$79.37	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3062				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	57
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.32	$80.88	$89.43	$98.48	$107.21	$114.31	See Web	

RG217/U Coax, 50 Ohm

Part No. PE3997				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.	5.8 dB/100ft	260 W	58
12"	24"	36"	48"	60"	72"	Custom Len.	
$107.34	$112.45	$117.57	$122.98	$128.19	$125.23	See Web	

RG218/U Coax, 50 Ohm

Part No. PE33236				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.87" dia.	5 dB/100ft	600 W	59
12"	24"	36"	48"	60"	72"	Custom Len.	
$251.92	$280.25	$276.84	$307.45	$301.78	$334.40	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3447				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	60
6"	12"	18"	24"	30"	36"	Custom Len.	
$51.08	$53.13	$54.35	$56.06	$55.40	$59.49	See Web	
Part No. PE3W00417				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	61
12"	24"	36"	48"	60"	50CM	Custom Len.	
$52.55	$66.47	$70.03	$73.60	$77.16	$65.17	See Web	

RG225/U Coax, 50 Ohm

Part No. PE33269				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	62
12"	24"	36"	48"	60"	-	Custom Len.	
$96.43	$131.51	$178.04	$204.38	$240.80	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3487				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	63
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.24	$71.68	$69.54	$72.72	$82.26	$79.07	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE33288				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	64
12"	24"	36"	48"	60"	-	Custom Len.	
$58.54	$61.74	$64.95	$68.14	$71.34	-	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3607				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	65
12"	24"	36"	48"	60"	72"	Custom Len.	
$87.75	$105.79	$122.11	$140.93	$159.07	$177.20	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3653				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	66
12"	24"	36"	48"	60"	72"	Custom Len.	
$65.94	$74.08	$82.20	$90.81	$99.09	$107.39	See Web	

PE-B400 Coax, 50 Ohm

Part No. PE3629				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.403" dia.	6 dB/100ft	190 W	67
12"	24"	36"	48"	60"	-	Custom Len.	
$58.64	$60.52	$62.35	$64.21	$66.06	-	See Web	

PE-P141 Coax, 50 Ohm

Part No. PE302				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			68
12"	24"	36"	48"	60"	72"	Custom Len.	
$184.39	$196.69	$209.00	$222.04	$234.58	$257.56	See Web	
Part No. PE352				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.	11.2 dB/100ft	600 W	69
12"	24"	36"	48"	60"	72"	Custom Len.	
$134.39	$146.70	$158.99	$172.03	$184.58	$185.55	See Web	

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1047				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			70
12"	24"	36"	50CM	100CM	-	Custom Len.	
$98.74	$116.33	$135.28	$109.51	$140.58	-	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE33377				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	71
12"	24"	36"	48"	60"	-	Custom Len.	
$60.51	$71.01	$81.54	$92.69	$103.44	-	See Web	

LMR-400-UF Coax, 50 Ohm

Part No. PE3C0218				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	5 dB/100ft		72
12"	24"	36"	48"	60"	300"	Custom Len.	
$56.29	$56.94	$59.75	$62.57	$65.38	Call	See Web	

PE-FF430 Coax, 50 Ohm

Part No. PE3C4002				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			73
60"	144"	-	-	-	-	Custom Len.	
$536.42	$791.30	-	-	-	-	See Web	
Part No. PE3C4005				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			74
60"	100CM	-	-	-	-	Custom Len.	
Call	$648.53	-	-	-	-	See Web	

Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

For our complete selection of cable assemblies, please visit our website

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA1803				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			75
24"	36"	48"	60"	-	-	Custom Len.	
$858.46	$996.04	$954.71	$1,101.64	-	-	See Web	

RG55B/U Coax, 53 Ohm

Part No. PE3499				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	76
12"	24"	36"	48"	60"	72"	Custom Len.	
$52.17	$54.17	$56.62	$59.09	$61.55	$64.02	See Web	

RG11A/U Coax, 75 Ohm

Part No. PE33479				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W	77
12"	24"	36"	48"	60"	-	Custom Len.	
$72.03	$74.31	$71.74	$73.61	$75.51	-	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE36181				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	78
12"	24"	36"	48"	60"	-	Custom Len.	
$42.46	$43.86	$45.19	$46.59	$47.96	-	See Web	

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0008				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			79
12"	18"	24"	30"	36"	48"	Custom Len.	
$181.26	$167.73	$170.69	$173.64	$176.60	$182.52	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0036				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			80
12"	18"	24"	30"	36"	48"	Custom Len.	
$186.38	$174.73	$180.01	$185.30	$191.23	$201.16	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0064				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			81
12"	18"	24"	30"	36"	48"	Custom Len.	
$166.39	$170.15	$173.91	$177.67	$181.44	$188.96	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE34142				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	40 dB/100ft	32 W	82
6"	12"	18"	24"	36"	48"	Custom Len.	
$100.32	$110.61	$109.74	$122.60	$125.88	$136.60	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE34144				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	83
6"	12"	18"	24"	36"	48"	Custom Len.	
$99.73	$104.56	$107.94	$112.67	$122.17	$131.73	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34138				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					13 dB/100ft	450 W	84
6"	12"	18"	24"	36"	48"	Custom Len.	
$87.21	$92.64	$98.23	$97.43	$107.45	$115.86	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34140				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	85
6"	12"	18"	24"	36"	48"	Custom Len.	
$107.67	$112.20	$116.75	$121.26	$130.36	$139.40	See Web	

RG401/U Coax, 50 Ohm

Part No. PE3782				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	1,400 W	86
6"	12"	18"	24"	36"	48"	Custom Len.	
$151.35	$151.35	$163.26	$175.13	$198.94	$235.59	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3827				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	87
6"	12"	18"	24"	36"	48"	Custom Len.	
$90.26	$90.26	$99.98	$104.28	$106.33	$112.77	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3920				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	88
6"	12"	18"	24"	36"	48"	Custom Len.	
$106.75	$110.32	$113.97	$117.55	$133.03	$132.00	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE3995				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	89
6"	12"	18"	24"	36"	48"	Custom Len.	
$147.16	$155.98	$157.00	$166.83	$186.51	$206.18	See Web	

N MALE TO N MALE RIGHT ANGLE

Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE345				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft	820 W	90
12"	24"	36"	48"	60"	50CM	Custom Len.	
$241.42	$259.02	$276.63	$294.23	$311.83	$252.71	See Web	

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38934				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		91
12"	24"	36"	48"	60"	-	Custom Len.	
$59.57	$60.88	$62.20	$63.54	$64.86	-	See Web	

PE-C195 Coax, 50 Ohm

Part No. PE37944				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	92
36"	48"	60"	72"	120"	-	Custom Len.	
$55.70	$56.49	$57.24	$58.04	$61.19	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE37945				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	93
36"	48"	60"	72"	120"	-	Custom Len.	
$67.14	$68.21	$69.28	$72.15	$83.87	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE37946				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	94
36"	48"	60"	72"	120"	-	Custom Len.	
$95.42	$97.15	$98.80	$102.21	$107.15	-	See Web	

PE-C600 Coax, 50 Ohm

Part No. PE37947				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.7 dB/100ft	900 W	95
36"	48"	60"	72"	120"	-	Custom Len.	
$134.77	$137.44	$148.73	$142.81	$153.55	-	See Web	

LMR-400 Coax, 50 Ohm

Part No. PE3C0041				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		96
12"	24"	36"	48"	60"	-	Custom Len.	
$85.83	$82.51	$84.00	$90.49	$92.02	-	See Web	

Part No. PE3C0106				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		97
12"	24"	36"	48"	60"	-	Custom Len.	
$88.53	$90.06	$88.98	$90.49	$94.73	-	See Web	

Part No. PE3W00430				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		98
12"	24"	36"	48"	60"	50CM	Custom Len.	
$82.96	$84.34	$85.71	$87.07	$88.45	$83.85	See Web	

LMR-400-DB Coax, 50 Ohm

Part No. PE3W01127				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.15 dB/100ft		99
12"	24"	36"	48"	60"	50CM	Custom Len.	
$78.40	$79.98	$81.57	$83.16	$84.74	$79.41	See Web	

LMR-600 Coax, 50 Ohm

Part No. PE3C0050				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft		1
12"	24"	36"	48"	60"	-	Custom Len.	
$122.42	$125.48	$121.63	$124.71	$127.77	-	See Web	

Part No. PE3C0111				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft		2
12"	24"	36"	48"	60"	-	Custom Len.	
$115.56	$112.10	$121.71	$118.22	$128.09	-	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5285				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			3
12"	24"	36"	48"	60"	50CM	Custom Len.	
$286.46	$308.91	$331.37	$353.83	$376.28	$300.85	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0176				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			4
12"	18"	24"	36"	48"	60"	Custom Len.	
$525.93	$535.12	$544.31	$562.70	$581.08	$599.46	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0221				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			5
8"	12"	18"	24"	30"	36"	Custom Len.	
$475.62	$480.94	$488.90	$496.87	$504.85	$512.81	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0249				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			6
12"	18"	24"	36"	48"	60"	Custom Len.	
$610.40	$625.74	$641.09	$671.78	$702.46	$733.14	See Web	

Precision Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39453				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	7
6"	9"	12"	18"	24"	-	Custom Len.	
$64.38	$66.53	$63.61	$91.70	$97.54	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-SR405FL Coax, 50 Ohm

Part No. PE39445				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	8
6"	9"	12"	18"	24"	-	Custom Len.	
$57.76	$60.80	Call	Call	Call	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39459				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	9
6"	9"	12"	18"	24"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7843				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		10
12"	50CM	24"	36"	48"	60"	Custom Len.	
$61.96	$64.35	$65.69	$69.42	$73.14	$76.87	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6205				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	11
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.24	$66.37	$72.49	$78.63	$84.76	$64.16	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C6346				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			12
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.24	$56.04	$58.32	$60.61	$62.89	$55.21	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C6361				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			13
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.49	$57.50	$60.53	$63.54	$66.54	$56.42	See Web	

SPO-500 Coax, 50 Ohm

Part No. PE3C6372				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.53" dia.			14
12"	24"	36"	48"	60"	50CM	Custom Len.	
$44.89	$48.00	$51.12	$54.22	$56.82	$46.90	See Web	

SPF-500 Coax, 50 Ohm

Part No. PE3C6375				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.			15
12"	24"	36"	48"	60"	50CM	Custom Len.	
$46.20	$50.64	$54.56	$58.94	$63.33	$49.04	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3240				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		16
12"	24"	36"	48"	60"	50CM	Custom Len.	
$271.97	$300.09	$328.20	$356.32	$384.45	$289.98	See Web	

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39467				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	17
6"	9"	12"	18"	24"	-	Custom Len.	
$90.58	$93.79	$90.58	$100.59	Call	-	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3699				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	18
12"	24"	36"	48"	60"	72"	Custom Len.	
$90.13	$97.11	$100.49	$104.06	$102.58	$105.70	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3143				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	19
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.17	$74.08	$69.37	$70.18	$70.98	$71.79	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3726				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	20
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.42	$78.88	$85.56	$92.63	$99.44	$100.94	See Web	

Part No. PE3W06863				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			21
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.97	$70.46	$76.94	$83.43	$89.93	$68.13	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE34205				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	22
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.69	$71.18	$71.65	$72.13	$72.60	$73.07	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34212				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	23
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.58	$70.91	$73.28	$75.58	$77.96	$80.34	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3797				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	24
12"	24"	36"	48"	60"	72"	Custom Len.	
$90.55	$97.95	$99.92	$101.99	$97.86	$106.00	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3071				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	25
12"	24"	36"	48"	60"	72"	Custom Len.	
$107.77	$114.71	$123.13	$126.01	$140.66	$149.26	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3168				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	26
12"	24"	36"	48"	60"	72"	Custom Len.	
$74.48	$72.15	$81.34	$84.97	$81.72	$91.95	See Web	

RG225/U Coax, 50 Ohm

Part No. PE34203				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	27
12"	24"	36"	48"	60"	72"	Custom Len.	
$126.53	$161.86	$197.20	$232.53	$267.85	$303.19	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34210				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	28
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.69	$76.87	$84.99	$83.22	$86.39	$95.62	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34207				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	29
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.44	$72.68	$75.86	$79.09	$82.32	$85.54	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3255				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	30
12"	24"	36"	48"	60"	72"	Custom Len.	
$106.63	$129.24	$147.04	$165.86	$183.99	$202.12	See Web	

RG400/U Coax, 50 Ohm

Part No. PE33321				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	31
12"	24"	36"	48"	60"	72"	Custom Len.	
$79.49	$92.39	$100.52	$107.61	$108.61	$123.95	See Web	

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1048				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			32
12"	24"	36"	75"	50CM	100CM	Custom Len.	
$95.75	$108.57	$126.26	Call	$103.64	$131.22	See Web	

PE-1/2 Helical Coax, 50 Ohm

Part No. PE37970				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.54" dia.			33
36"	72"	-	-	-	-	Custom Len.	
$128.51	$170.30	-	-	-	-	See Web	

LMR-400 Coax, 50 Ohm

Part No. PE3C7931				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		34
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.09	$61.45	$62.81	$64.17	$65.53	$59.59	See Web	

LMR-400-UF Coax, 50 Ohm

Part No. PE3C3643				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	5 dB/100ft		35
12"	24"	36"	48"	60"	50CM	Custom Len.	
$61.87	$61.19	$63.98	$66.80	$69.61	$60.17	See Web	

PE-FF430 Coax, 50 Ohm

Part No. PE3C4003				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			36
60"	144"	-	-	-	-	Custom Len.	
$824.84	$1,136.07	-	-	-	-	See Web	

Part No. PE3C4006				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			37
60"	100CM	-	-	-	-	Custom Len.	
Call	$871.78	-	-	-	-	See Web	

N MALE TO N FEMALE

Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4138				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	38
12"	24"	36"	48"	60"	50CM	Custom Len.	
$96.43	$102.56	$107.19	$113.24	$119.30	$100.37	See Web	

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE37948				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	39
36"	48"	60"	72"	120"	-	Custom Len.	
$36.51	$35.19	$35.99	$36.77	$39.93	-	See Web	

Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

For our complete selection of cable assemblies, please visit our website

PE-C240 Coax, 50 Ohm

Part No. PE37949				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	40
36"	48"	60"	72"	120"	-	Custom Len.	
$52.54	$53.61	$54.19	$55.26	$59.51	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE34716				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	41
12"	24"	36"	48"	60"	-	Custom Len.	
$73.21	$74.61	$75.98	$77.37	$84.27	-	See Web	
Part No. PE37950				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	42
36"	48"	60"	72"	120"	-	Custom Len.	
$76.44	$77.88	$79.32	$80.78	$86.57	-	See Web	

PE-C600 Coax, 50 Ohm

Part No. PE37951				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.7 dB/100ft	900 W	43
36"	48"	72"	120"	300CM	-	Custom Len.	
$119.31	$121.90	$135.45	$137.45	$141.22	-	See Web	

LMR-400 Coax, 50 Ohm

Part No. PE3W00676				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.			44
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.02	$64.49	$65.96	$67.44	$68.91	$63.96	See Web	

PE-SF200LL Coax, 50 Ohm

Part No. PE3TC1103				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.185" dia.			45
24"	36"	48"	72"	100CM	200CM	Custom Len.	
$83.29	$95.68	$106.56	$130.97	$99.15	$137.83	See Web	

Precision Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39454				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	46
6"	9"	12"	18"	24"	-	Custom Len.	
$88.29	Call	Call	Call	Call	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE39446				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	47
6"	9"	12"	18"	24"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

PE-80TEST Coax, 50 Ohm

Part No. PE3TC0104				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			48
24"	48"	72"	-	-	-	Custom Len.	
$416.24	$509.19	$602.16	-	-	-	See Web	

Low PIM Formable Cable Assemblies

PE-SR402FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2001				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.			49
100CM	200CM	-	-	-	-	Custom Len.	
$80.05	$102.52	-	-	-	-	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7844				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		50
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.21	$62.95	$66.67	$70.40	$74.13	$61.60	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6200				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	51
12"	24"	36"	48"	60"	50CM	Custom Len.	
$57.61	$63.75	$69.88	$76.00	$82.14	$61.52	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE331				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	4.6 dB/100ft		52
12"	24"	36"	48"	60"	50CM	Custom Len.	
$426.07	$454.22	$458.19	$486.33	$514.44	$419.98	See Web	
Part No. PE3C3241				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		53
12"	24"	36"	48"	60"	50CM	Custom Len.	
$251.68	$279.01	$306.34	$333.65	$360.99	$269.18	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34291				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	54
6"	12"	18"	24"	36"	48"	Custom Len.	
$106.85	$109.22	$113.12	$116.96	$124.72	$132.45	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34293				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	55
6"	12"	18"	24"	36"	48"	Custom Len.	
$108.77	$116.81	$124.97	$133.02	$149.23	$165.42	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE3485				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	56
6"	12"	18"	24"	36"	48"	Custom Len.	
$92.34	$96.36	$100.41	$109.49	$110.86	$118.77	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3965				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	57
6"	12"	18"	24"	36"	48"	Custom Len.	
$102.12	$107.85	$111.94	$117.61	$128.80	$140.06	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3714				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	58
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.19	$61.58	$62.47	$58.61	$59.43	$60.24	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3996				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	59
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.11	$66.79	$73.48	$80.54	$87.34	$94.17	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34283				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	60
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.96	$69.39	$71.84	$74.29	$76.72	$79.16	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3232				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	9 dB/100ft	190 W	61
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.38	$74.34	$76.30	$78.39	$80.39	$82.39	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3650				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	62
12"	24"	36"	48"	60"	72"	Custom Len.	
$79.13	$87.68	$96.24	$105.28	$106.87	$121.02	See Web	

RG217/U Coax, 50 Ohm

Part No. PE34274				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.	5.8 dB/100ft	260 W	63
12"	24"	36"	48"	60"	72"	Custom Len.	
$139.43	$144.21	$149.00	$153.76	$158.54	$163.31	See Web	

RG218/U Coax, 50 Ohm

Part No. PE34276				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.87" dia.	3.8 dB/100ft	560 W	64
12"	24"	36"	48"	60"	72"	Custom Len.	
$208.45	$220.57	$232.59	$244.69	$256.80	$288.30	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3667				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	65
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.67	$54.77	$57.96	$65.13	$68.63	$72.13	See Web	

RG225/U Coax, 50 Ohm

Part No. PE33728				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	66
12"	24"	36"	48"	60"	72"	Custom Len.	
$96.84	$130.83	$166.14	$201.48	$236.82	$272.13	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3986				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	67
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.95	$75.46	$74.31	$77.47	$80.65	$83.82	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34281				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	26.1 dB/100ft	160 W	68
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.85	$66.10	$69.25	$72.48	$75.71	$78.94	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3977				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W	69
12"	24"	36"	48"	60"	72"	Custom Len.	
$87.82	$105.86	$122.17	$141.00	$148.77	$165.54	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3617				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	70
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.54	$77.67	$85.80	$94.40	$102.70	$103.91	See Web	
Part No. PE3W07899				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	71
12"	18"	24"	36"	48"	60"	Custom Len.	
$67.01	$68.52	$72.55	$80.61	$88.67	$96.73	See Web	

PE-1/2 Helical Coax, 50 Ohm

Part No. PE37969				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.54" dia.			72
36"	72"	-	-	-	-	Custom Len.	
$127.71	$156.16	-	-	-	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For Custom Lengths, Metric Lengths or Special Configurations, Please call (949) 261-1920

PE-FF430 Coax, 50 Ohm

Part No. PE3C4004				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			73
60"	144"	-	-	-	-	Custom Len.	
$536.42	$791.30	-	-	-	-	See Web	

Part No. PE3C4007				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			74
60"	100CM	-	-	-	-	Custom Len.	
Call	$690.69	-	-	-	-	See Web	

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA1804				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			75
24"	48"	-	-	-	-	Custom Len.	
$874.60	$971.42	-	-	-	-	See Web	

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0009				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			76
12"	18"	24"	30"	36"	48"	Custom Len.	
$175.15	$178.12	$181.08	$184.03	$186.99	$192.91	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0037				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			77
12"	18"	24"	30"	36"	48"	Custom Len.	
$179.83	$185.11	$190.41	$195.68	$200.98	$211.56	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0065				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			78
12"	18"	24"	30"	36"	48"	Custom Len.	
$176.77	$180.53	$184.29	$188.06	$191.82	$199.34	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE34287				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	79
6"	12"	18"	24"	36"	48"	Custom Len.	
$106.88	$112.20	$117.61	$123.02	$133.75	$144.55	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE34296				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	80
6"	12"	18"	24"	36"	48"	Custom Len.	
$107.72	$111.04	$115.80	$120.55	$130.08	$139.61	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34289				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	81
6"	12"	18"	24"	36"	48"	Custom Len.	
$93.40	$98.43	$103.44	$106.93	$116.81	$126.73	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34285				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	82
6"	12"	18"	24"	36"	48"	Custom Len.	
$101.05	$105.59	$108.69	$113.27	$122.30	$131.42	See Web	

RG401/U Coax, 50 Ohm

Part No. PE3979				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	83
6"	12"	18"	24"	36"	48"	Custom Len.	
$112.20	$123.72	$135.30	$146.82	$185.23	$193.03	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3829				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	84
6"	12"	18"	24"	36"	48"	Custom Len.	
$101.94	$101.94	$105.96	$108.44	$116.37	$124.28	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3921				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	85
6"	12"	18"	24"	36"	48"	Custom Len.	
$97.36	$101.00	$104.69	$106.82	$114.03	$121.26	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE3988				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	86
6"	12"	18"	24"	36"	48"	Custom Len.	
$110.19	$119.69	$129.25	$138.76	$157.83	$176.88	See Web	

Standard Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C0125				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		87
12"	24"	36"	48"	60"	-	Custom Len.	
$131.49	$134.25	$137.03	$139.80	$142.58	-	See Web	

N MALE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Flexible Cable Assemblies

LMR-400-UF Coax, 50 Ohm

Part No. PE3W02547				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	5 dB/100ft		88
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.12	$71.58	$74.46	$77.35	$80.25	$70.55	See Web	

Low Loss Flexible Cable Assemblies

PE-C240 Coax, 50 Ohm

Part No. PE38672				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	89
36"	48"	60"	72"	120"	-	Custom Len.	
$58.23	$55.78	$57.77	$62.09	$73.21	-	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE344				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		90
12"	24"	36"	48"	60"	50CM	Custom Len.	
$198.22	$215.83	$233.43	$251.03	$268.63	$209.49	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5257				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			91
12"	24"	36"	48"	60"	50CM	Custom Len.	
$251.25	$273.71	$296.15	$318.61	$341.07	$265.63	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0175				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			92
12"	18"	24"	36"	48"	60"	Custom Len.	
$495.75	$504.94	$514.13	$532.53	$550.90	$569.29	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0220				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			93
8"	12"	18"	24"	30"	36"	Custom Len.	
$479.88	$485.20	$493.16	$501.13	$508.70	$517.07	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0248				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			94
12"	18"	24"	36"	48"	60"	Custom Len.	
$535.30	$550.64	$565.99	$596.67	$627.35	$658.04	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7845				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		95
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.21	$62.95	$66.67	$70.40	$74.13	$61.60	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6201				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	96
12"	24"	36"	48"	60"	50CM	Custom Len.	
$57.61	$63.75	$69.88	$76.00	$82.14	$61.52	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34156				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	97
6"	12"	18"	24"	36"	48"	Custom Len.	
$107.35	$111.23	$115.07	$118.98	$126.73	$134.47	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34150				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	98
6"	12"	18"	24"	36"	48"	Custom Len.	
$110.32	$118.44	$126.53	$134.65	$150.85	$167.06	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE3488				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	99
6"	12"	18"	24"	36"	48"	Custom Len.	
$100.83	$100.83	$104.97	$107.59	$115.78	$123.95	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3971				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	1
6"	12"	18"	24"	36"	48"	Custom Len.	
$106.75	$112.34	$118.01	$123.61	$134.86	$146.11	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3966				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	2
12"	24"	36"	48"	60"	72"	Custom Len.	
$87.91	$86.04	$89.15	$92.28	$95.39	$98.50	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3320				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	3
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.60	$62.50	$59.73	$64.35	$61.35	$62.16	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3034				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		4
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.04	$69.73	$76.41	$83.49	$90.29	$97.11	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

RG178B/U Coax, 50 Ohm

Part No. PE34201				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	5
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.37	$78.42	$79.48	$80.53	$81.60	$82.65	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34181				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	6
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.25	$71.62	$73.93	$76.32	$78.69	$80.98	See Web	

RG213/U Coax, 50 Ohm

Part No. PE33543				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	7
12"	24"	36"	48"	60"	72"	Custom Len.	
$81.67	$83.49	$85.32	$87.14	$88.98	$90.80	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3217				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	8
12"	24"	36"	48"	60"	72"	Custom Len.	
$76.56	$85.36	$94.17	$102.97	$110.22	$118.91	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3686				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	9
12"	24"	36"	48"	60"	72"	Custom Len.	
$57.48	$60.68	$63.87	$72.55	$70.23	$79.53	See Web	

RG225/U Coax, 50 Ohm

Part No. PE34194				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	10
12"	24"	36"	48"	60"	72"	Custom Len.	
$95.84	$129.86	$165.20	$200.51	$235.85	$271.19	See Web	

RG316/U Coax, 50 Ohm

Part No. PE33534				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	11
12"	24"	36"	48"	60"	72"	Custom Len.	
$74.46	$77.64	$80.82	$84.00	$92.95	$90.33	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34198				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	26.1 dB/100ft	160 W	12
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.11	$73.35	$76.58	$79.80	$83.02	$86.21	See Web	

RG393/U Coax, 50 Ohm

Part No. PE33530				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	13
12"	24"	36"	48"	60"	72"	Custom Len.	
$80.19	$97.19	$112.61	$129.38	$146.14	$162.92	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3227				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	14
12"	24"	36"	48"	60"	72"	Custom Len.	
$75.01	$83.15	$84.77	$99.88	$100.11	$114.84	See Web	

PE-P141 Coax, 50 Ohm

Part No. PE3C3255				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.	11.2 dB/100ft	550 W	15
12"	24"	36"	48"	60"	50CM	Custom Len.	
$91.65	$103.76	$114.28	$126.23	$138.18	$99.41	See Web	

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0010				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			16
12"	18"	24"	30"	36"	48"	Custom Len.	
$179.33	$182.28	$185.24	$188.20	$191.16	$197.07	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0038				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			17
12"	18"	24"	30"	36"	48"	Custom Len.	
$183.99	$189.28	$194.58	$199.85	$205.15	$215.73	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0066				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			18
12"	18"	24"	30"	36"	48"	Custom Len.	
$180.94	$184.67	$188.46	$192.23	$196.00	$203.52	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE34152				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	19
6"	12"	18"	24"	36"	48"	Custom Len.	
$108.83	$114.23	$119.62	$124.97	$135.77	$146.51	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE34154				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	20
6"	12"	18"	24"	36"	48"	Custom Len.	
$108.25	$112.99	$117.80	$122.55	$132.06	$141.62	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34158				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	21
6"	12"	18"	24"	36"	48"	Custom Len.	
$103.00	$103.00	$106.68	$111.78	$121.98	$132.18	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34161				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	22
6"	12"	18"	24"	36"	48"	Custom Len.	
$107.13	$110.19	$114.74	$119.23	$128.36	$137.40	See Web	

RG401/U Coax, 50 Ohm

Part No. PE3983				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	23
6"	12"	18"	24"	36"	48"	Custom Len.	
$132.81	$132.81	$144.70	$156.59	$180.39	$204.18	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3830				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	24
6"	12"	18"	24"	36"	48"	Custom Len.	
$93.12	$93.12	$97.15	$107.30	$107.68	$115.58	See Web	
Part No. PE3C3286				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	25
12"	50CM	24"	36"	100CM	48"	Custom Len.	
$81.90	$82.61	$85.62	$93.96	$96.31	$102.31	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3922				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	26
6"	12"	18"	24"	36"	48"	Custom Len.	
$117.78	$114.80	$125.72	$122.26	$129.71	$137.16	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE3993				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	27
6"	12"	18"	24"	36"	48"	Custom Len.	
$111.76	$121.33	$130.83	$140.39	$159.45	$178.52	See Web	

N MALE TO N FEMALE 4 HOLE FLANGE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3W02012				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		28
12"	24"	36"	48"	60"	50CM	Custom Len.	
$52.04	$52.85	$53.65	$54.46	$54.76	$52.56	See Web	

N MALE TO 4.1/9.5 MINI DIN MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4140				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			29
12"	24"	36"	48"	60"	50CM	Custom Len.	
$99.02	$105.15	$109.74	$115.79	$121.84	$102.94	See Web	

N MALE TO 4.3-10 MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4141				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	30
"	12"	24"	36"	48"	60"	Custom Len.	
Call	$99.02	$105.15	$109.74	$115.79	$121.84	See Web	

N MALE TO 7/16 DIN MALE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE39143				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	31
12"	24"	36"	48"	60"	-	Custom Len.	
$136.66	$137.40	$138.11	$138.83	$139.54	-	See Web	

PE-C600 Coax, 50 Ohm

Part No. PE38436				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.7 dB/100ft	900 W	32
36"	48"	60"	72"	120"	-	Custom Len.	
$132.25	$138.63	$144.99	$149.18	$176.88	-	See Web	

LMR-400 Coax, 50 Ohm

Part No. PE3W03803				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		33
12"	24"	36"	48"	60"	50CM	Custom Len.	
$93.76	$95.23	$96.71	$98.18	$99.66	$94.71	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

Low PIM Formable Cable Assemblies

PE-SR401FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2012				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.276" dia.			34
100CM	200CM	800CM	-	-	-	Custom Len.	
$166.50	$200.98	Call	-	-	-	See Web	

PE-SR402FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2002				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.			35
100CM	200CM	300CM	-	-	-	Custom Len.	
$121.23	$146.05	Call	-	-	-	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4132				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			36
12"	24"	36"	48"	60"	50CM	Custom Len.	
$101.58	$107.71	$112.27	$118.32	$124.37	$105.50	See Web	

Standard Formable Cable Assemblies

PE-SR401FL Coax, 50 Ohm

Part No. PE36178				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	37
12"	24"	36"	48"	60"	72"	Custom Len.	
$232.26	$248.47	$264.66	$280.87	$297.05	$313.27	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE35965				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	38
12"	24"	36"	48"	60"	72"	Custom Len.	
$205.53	$213.45	$221.32	$229.28	$237.14	$245.07	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE35284				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	39
12"	24"	36"	48"	60"	72"	Custom Len.	
$177.37	$180.44	$194.68	$186.58	$189.65	$192.72	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3207				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	40
12"	24"	36"	48"	60"	72"	Custom Len.	
$155.51	$156.30	$157.10	$157.90	$158.69	$159.49	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3216				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		41
12"	24"	36"	48"	60"	72"	Custom Len.	
$85.36	$91.68	$103.86	$104.27	$109.04	$115.25	See Web	

RG213/U Coax, 50 Ohm

Part No. PE34098				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	42
12"	24"	36"	48"	60"	72"	Custom Len.	
$176.13	$177.92	$179.73	$181.52	$183.33	$196.58	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3218				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	43
12"	24"	36"	48"	60"	72"	Custom Len.	
$180.69	$188.63	$204.78	$213.72	$222.32	$220.40	See Web	

RG217/U Coax, 50 Ohm

Part No. PE36170				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.	5.8 dB/100ft	260 W	44
12"	24"	36"	48"	60"	72"	Custom Len.	
$213.98	$218.79	$223.62	$228.44	$233.23	$238.05	See Web	

RG218/U Coax, 50 Ohm

Part No. PE36172				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.87" dia.	3.8 dB/100ft	560 W	45
12"	24"	36"	48"	60"	72"	Custom Len.	
$296.94	$309.05	$321.08	$355.17	$345.29	$357.39	See Web	

RG223/U Coax, 50 Ohm

Part No. PE33144				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	46
12"	24"	36"	48"	60"	72"	Custom Len.	
$82.29	$85.48	$88.66	$91.86	$95.03	$98.22	See Web	

RG393/U Coax, 50 Ohm

Part No. PE34357				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W	47
12"	24"	36"	48"	60"	72"	Custom Len.	
$190.13	$206.90	$223.68	$240.44	$274.07	$273.98	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34359				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	48
12"	24"	36"	48"	60"	72"	Custom Len.	
$94.04	$101.70	$107.85	$115.41	$122.97	$130.51	See Web	

PE-FF430 Coax, 50 Ohm

Part No. PE3C4000				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			49
60"	144"	-	-	-	-	Custom Len.	
$657.16	$861.72	-	-	-	-	See Web	

Standard Semi-Rigid Cable Assemblies

RG402/U Coax, 50 Ohm

Part No. PE35963				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	50
12"	24"	36"	48"	60"	72"	Custom Len.	
$205.25	$212.92	$220.62	$228.27	$235.97	$243.66	See Web	

N MALE TO 7/16 DIN MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4136				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			51
12"	24"	36"	48"	60"	50CM	Custom Len.	
$124.12	$118.89	$124.94	$130.98	$137.03	$116.71	See Web	

N MALE TO 7/16 DIN FEMALE

Low PIM Formable Cable Assemblies

PE-SR401FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2014				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.276" dia.			52
100CM	200CM	-	-	-	-	Custom Len.	
$159.38	$190.16	-	-	-	-	See Web	

PE-SR402FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2005				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.			53
100CM	200CM	-	-	-	-	Custom Len.	
$130.00	$154.79	-	-	-	-	See Web	

Standard Flexible Cable Assemblies

PE-FF430 Coax, 50 Ohm

Part No. PE3C4001				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			54
60"	144"	-	-	-	-	Custom Len.	
$928.81	$1,157.97	-	-	-	-	See Web	

N MALE TO BNC MALE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE36065				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	55
12"	24"	36"	48"	60"	-	Custom Len.	
$40.28	$38.09	$42.01	$39.67	$43.81	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE35269				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	56
12"	24"	36"	48"	60"	-	Custom Len.	
$56.54	$57.78	$56.52	$60.36	$62.67	-	See Web	

LMR-240-UF Coax, 50 Ohm

Part No. PE3C2404				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft		57
12"	24"	36"	48"	60"	50CM	Custom Len.	
$42.53	$42.35	$43.82	$45.28	$46.74	$41.82	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3252				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	58
12"	24"	36"	48"	60"	72"	Custom Len.	
$71.94	$74.99	$83.00	$80.98	$90.02	$87.00	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3042				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	59
12"	24"	36"	48"	60"	72"	Custom Len.	
$44.90	$45.73	$46.54	$47.35	$48.18	$49.00	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3W00140				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	60
12"	24"	36"	48"	60"	50CM	Custom Len.	
$45.67	$52.22	$58.23	$64.71	$71.20	$49.86	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3378				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	61
6"	12"	18"	24"	36"	48"	Custom Len.	
$45.73	$45.99	$46.23	$51.22	$46.96	$52.55	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3C3379				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	62
12"	24"	36"	48"	60"	72"	Custom Len.	
$47.78	$50.09	$52.39	$54.13	$56.43	$58.64	See Web	

Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

RG213/U Coax, 50 Ohm

Part No. PE3750				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	63
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$81.02	$82.97	$84.95	$81.91	$83.75	$91.04	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3097				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	64
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$86.76	$95.31	$103.87	$111.34	$112.48	$128.55	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3476				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	65
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$44.37	$47.83	$51.28	$54.44	$57.93	$61.42	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C3380				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	66
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.28	$58.71	$62.14	$61.67	$64.85	$72.79	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3254				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	67
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$89.84	$101.91	$117.41	$134.34	$151.26	$179.24	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3874				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	68
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.53	$67.67	$75.80	$84.41	$92.68	$100.98	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3CA1074				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	69
1 piece price shown. See web or call for volume pricing.				0.24" dia.			
12"	24"	36"	48"	60"	72"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

LMR-400-UF Coax, 50 Ohm

Part No. PE3CA1075				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	70
1 piece price shown. See web or call for volume pricing.				0.405" dia.			
12"	24"	36"	48"	60"	72"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

RG55B/U Coax, 53 Ohm

Part No. PE3477				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	71
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$42.61	$45.11	$47.59	$53.95	$52.56	$54.54	See Web	

N MALE TO BNC MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

LMR-240-UF Coax, 50 Ohm

Part No. PE3W04585				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	72
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.54	$55.97	$56.68	$58.12	$59.55	$54.74	See Web	

N MALE TO BNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE34882				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	73
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$72.40	$80.52	$88.66	$97.26	$105.54	-	See Web	

N MALE TO C FEMALE

Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE3W06365				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	74
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$122.79	$129.18	$135.58	$141.98	$148.38	$126.88	See Web	

N MALE TO GR874 SEXLESS

Standard Flexible Cable Assemblies

RG214/U Coax, 50 Ohm

Part No. PE3133				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	75
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$146.82	$154.83	$162.83	$170.84	$178.82	$186.85	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3170				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	76
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.99	$66.21	$69.37	$72.61	$75.86	$79.03	See Web	

N MALE TO MCX PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

RG316-DS Coax, 50 Ohm

Part No. PE35276				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	77
1 piece price shown. See web or call for volume pricing.				0.114" dia.	26.1 dB/100ft	160 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.29	$78.80	$82.31	$85.82	$89.33	$74.03	See Web	

N MALE TO MINI UHF MALE

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3282				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	78
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$45.36	$49.89	$50.80	$47.82	$52.67	$49.45	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3285				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	79
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		
12"	24"	36"	48"	60"	72"	Custom Len.	
$47.79	$54.03	$60.71	$67.77	$74.60	$81.42	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3280				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	80
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$39.59	$42.80	$46.04	$49.32	$55.54	$55.27	See Web	

RG303/U Coax, 50 Ohm

Part No. PE3W04230				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	81
1 piece price shown. See web or call for volume pricing.				0.17" dia.	14 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$39.01	$46.62	$54.24	$61.32	$68.88	$43.89	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3288				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	82
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.54	$61.00	$68.67	$76.33	$84.00	$91.66	See Web	

N MALE TO QMA MALE

Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5868				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	83
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$82.91	$89.04	$95.17	$101.31	$107.44	$86.84	See Web	

N MALE TO QMA MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3C0049				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	84
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		
12"	24"	36"	48"	60"	-	Custom Len.	
$55.37	$56.18	$57.02	$57.88	$58.71	-	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5874				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	85
1 piece price shown. See web or call for volume pricing.				0.28" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$85.29	$91.43	$97.56	$103.70	$108.30	$89.23	See Web	

N MALE TO QMA FEMALE

Low PIM Corrugated Cable Assemblies

Continued on Next Page

See Our Website For Current Pricing & Real-Time Stock Availability!

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5862				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			86
12"	24"	36"	48"	60"	50CM	Custom Len.	
$78.96	$85.09	$91.22	$97.36	$103.49	$82.88	See Web	

N MALE TO QN MALE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38453				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	87
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.35	$71.12	$71.90	$77.18	$73.49	$78.94	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE38452				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	88
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.06	$64.25	$65.14	$71.50	$72.28	$73.07	See Web	

RG213/U Coax, 50 Ohm

Part No. PE38450				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	89
12"	24"	36"	48"	60"	72"	Custom Len.	
$113.32	$115.14	$116.96	$118.77	$120.55	$122.36	See Web	

RG223/U Coax, 50 Ohm

Part No. PE38451				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	90
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.00	$76.18	$79.37	$82.57	$85.76	$88.94	See Web	

N MALE TO QN MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38490				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	91
12"	24"	36"	48"	60"	72"	Custom Len.	
$74.40	$75.19	$75.97	$76.75	$77.54	$78.33	See Web	

LMR-195 Coax, 50 Ohm

Part No. PE3C0059				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		92
12"	24"	36"	48"	60"	-	Custom Len.	
$65.95	$66.74	$67.49	$68.25	$69.02	-	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE38489				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	93
12"	24"	36"	48"	60"	72"	Custom Len.	
$88.46	$89.27	$90.07	$90.88	$91.70	$92.51	See Web	

RG213/U Coax, 50 Ohm

Part No. PE38491				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	94
12"	24"	36"	48"	60"	72"	Custom Len.	
$100.00	$101.86	$103.68	$105.53	$107.31	$107.67	See Web	

RG223/U Coax, 50 Ohm

Part No. PE38492				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	95
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.80	$81.65	$85.08	$83.45	$86.61	$89.85	See Web	

N MALE TO SHV PLUG

Standard Flexible Cable Assemblies

RG223/U Coax, 50 Ohm

Part No. PE3W04051				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	96
12"	24"	36"	48"	60"	50CM	Custom Len.	
$67.73	$71.30	$74.87	$78.43	$82.00	$70.01	See Web	

N MALE TO SMA MALE

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C0253				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.32" dia.	7.2 dB/100ft		97
60"	72"	120"	-	-	-	Custom Len.	
$395.79	$435.11	$675.13	-	-	-	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5273				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			98
12"	24"	36"	48"	60"	50CM	Custom Len.	
$222.74	$245.21	$267.66	$290.11	$312.56	$237.13	See Web	

Low PIM Formable Cable Assemblies

PE-SR402FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2006				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.			99
30CM	45CM	50CM	-	100CM	150CM	Custom Len.	
Call	Call	Call	-	$84.33	Call	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5887				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			1
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.97	$81.10	$87.24	$93.37	$99.51	$78.90	See Web	

Part No. PE3C6213				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	2
12"	24"	36"	48"	60"	50CM	Custom Len.	
$52.84	$58.49	$64.62	$70.76	$76.88	$56.27	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE332				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	4.6 dB/100ft		3
12"	24"	36"	48"	60"	600"	Custom Len.	
$285.63	$313.74	$397.52	$369.99	$400.71	Call	See Web	

Part No. PE337				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			4
12"	24"	36"	48"	60"	72"	Custom Len.	
$275.96	$304.08	$332.20	$360.33	$388.43	$423.28	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3662				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	5
12"	24"	36"	48"	60"	72"	Custom Len.	
$47.04	$47.93	$49.65	$49.79	$51.26	$51.64	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3234				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		6
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.04	$57.48	$62.13	$64.55	$68.49	$71.55	See Web	

PE-P141 Coax, 50 Ohm

Part No. PE354				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.	11.2 dB/100ft	600 W	7
12"	24"	36"	48"	60"	72"	Custom Len.	
$181.19	$193.50	$205.82	$218.85	$231.40	$243.94	See Web	

PE-FF430 Coax, 50 Ohm

Part No. PE3C4008				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			8
60"	-	-	-	-	-	Custom Len.	
$747.71	-	-	-	-	-	See Web	

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA1805				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			9
24"	36"	48"	-	-	-	Custom Len.	
$943.23	$996.04	$1,048.84	-	-	-	See Web	

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0014				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			10
12"	18"	24"	30"	36"	48"	Custom Len.	
$200.91	$203.86	$206.82	$209.77	$212.73	$218.64	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0042				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			11
12"	18"	24"	30"	36"	48"	Custom Len.	
$205.57	$210.85	$216.14	$221.43	$226.72	$237.30	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0070				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			12
12"	18"	24"	30"	36"	48"	Custom Len.	
$202.51	$206.27	$210.03	$213.79	$217.56	$225.08	See Web	

Standard Semi-Rigid Cable Assemblies

RG401/U Coax, 50 Ohm

Part No. PE3W04229				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	1,400 W	13
12"	24"	36"	48"	60"	50CM	Custom Len.	
$112.05	$137.04	$161.99	$187.04	$212.04	$128.06	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3887				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.1 dB/100ft	450 W	14
6"	12"	18"	24"	36"	48"	Custom Len.	
$75.94	$74.18	$84.42	$88.72	$90.24	$98.26	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

N MALE TO SMA MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm — 15

Part No. PE3C5275				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$262.97	$285.44	$307.90	$330.36	$352.80	$277.36	See Web

LMR-240-UF Coax, 50 Ohm — 16

Part No. PE3W06417				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$58.84	$60.31	$61.80	$63.28	$64.77	$59.78	See Web

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm — 17

Part No. PE3C5892				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$76.57	$82.70	$88.83	$94.97	$101.10	$80.50	See Web

— 18

Part No. PE3C6212				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$57.61	$63.75	$69.88	$76.00	$82.14	$61.52	See Web

Standard Flexible Cable Assemblies

M17/60-RG142-27478 Coax, 50 Ohm — 19

Part No. PE3M0015				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.		
12"	18"	24"	30"	36"	48"	Custom Len.
$264.02	$242.97	$245.93	$248.90	$251.86	$258.65	See Web

M17/84-RG223-0XDS2 Coax, 50 Ohm — 20

Part No. PE3M0043				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.212" dia.		
12"	18"	24"	30"	36"	48"	Custom Len.
$244.69	$249.96	$255.26	$260.55	$265.84	$276.42	See Web

M17/128-RG400-27478 Coax, 50 Ohm — 21

Part No. PE3M0071				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.		
12"	18"	24"	30"	36"	48"	Custom Len.
$241.64	$245.39	$249.16	$252.91	$256.69	$264.21	See Web

N MALE TO SMA FEMALE

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm — 22

Part No. PE3C1128				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$170.95	$188.55	$206.16	$223.76	$241.37	$182.24	See Web

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm — 23

Part No. PE3C5881				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$75.78	$81.91	$88.05	$94.17	$100.30	$79.70	See Web

Standard Flexible Cable Assemblies

PE-FF430 Coax, 50 Ohm — 24

Part No. PE3C4009				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.43" dia.		
60"	-	-	-	-	-	Custom Len.
$747.71	-	-	-	-	-	See Web

PE-VNA-R Coax, 50 Ohm — 25

Part No. PE3VNA1806				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.43" dia.		
24"	36"	48"	-	-	-	Custom Len.
$943.23	$996.04	$1,048.84	-	-	-	See Web

N MALE TO SMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm — 26

Part No. PE3C5277				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$241.18	$263.65	$286.09	$308.56	$331.01	$255.57	See Web

N MALE TO SSMC PLUG

Flexible Cable Assemblies

RG316/U Coax, 50 Ohm — 27

Part No. PE3C4415				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
6"	12"	18"	24"	36"	48"	Custom Len.
$67.83	$76.30	$70.92	$72.43	$75.53	$78.60	See Web

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm — 28

Part No. PE3C4432				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
6"	12"	18"	24"	36"	48"	Custom Len.
$56.18	$62.26	$62.67	$57.40	$58.22	$59.02	See Web

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm — 29

Part No. PE3C4451				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	18"	24"	36"	48"	Custom Len.
$69.30	$73.44	$77.57	$81.71	$89.98	$98.24	See Web

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm — 30

Part No. PE3C4399				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
6"	12"	18"	24"	36"	48"	Custom Len.
$80.91	$81.44	$81.96	$82.44	$83.48	$84.50	See Web

N MALE TO SSMC PLUG RIGHT ANGLE

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm — 31

Part No. PE3C4433				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
6"	12"	18"	24"	36"	48"	Custom Len.
$52.88	$53.31	$53.72	$54.12	$54.45	$55.25	See Web

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm — 32

Part No. PE3C4489				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	18"	24"	36"	48"	Custom Len.
$65.88	$70.03	$74.17	$78.30	$86.58	$94.85	See Web

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm — 33

Part No. PE3C4467				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
6"	12"	18"	24"	36"	48"	Custom Len.
$71.66	$72.18	$72.69	$73.21	$74.22	$75.26	See Web

RG316/U Coax, 50 Ohm — 34

Part No. PE3C4416				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
6"	12"	18"	24"	36"	48"	Custom Len.
$64.04	$65.59	$67.13	$68.66	$71.76	$74.82	See Web

RG316-DS Coax, 50 Ohm — 35

Part No. PE3C4478				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W
6"	12"	18"	24"	36"	48"	Custom Len.
$63.95	$65.53	$67.07	$68.63	$71.74	$74.84	See Web

N MALE TO SSMC JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm — 36

Part No. PE3C4452				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	18"	24"	36"	48"	Custom Len.
$61.79	$65.93	$70.08	$74.20	$82.48	$90.76	See Web

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm — 37

Part No. PE3C4400				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
6"	12"	18"	24"	36"	48"	Custom Len.
$76.54	$84.76	$77.57	$85.92	$79.11	$80.14	See Web

See Our Website For Current Pricing & Real-Time Stock Availability!

N MALE TO TNC MALE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm — 38

Part No. PE35785				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W
12"	24"	36"	48"	60"	-	Custom Len.
$41.98	$42.78	$46.22	$47.14	$48.02	-	See Web

PE-C200 Coax, 50 Ohm — 39

Part No. PE36067				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10.8 dB/100ft	170 W
12"	24"	36"	48"	60"	-	Custom Len.
$59.63	$60.86	$65.56	$70.18	$63.37	-	See Web

PE-C240 Coax, 50 Ohm — 40

Part No. PE36958				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W
12"	24"	36"	48"	60"	-	Custom Len.
$54.35	$59.96	$61.20	$62.50	$63.79	-	See Web

PE-C400 Coax, 50 Ohm — 41

Part No. PE34801				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W
12"	24"	36"	48"	60"	-	Custom Len.
$78.16	$79.62	$84.29	$87.85	$94.86	-	See Web

LMR-400 Coax, 50 Ohm — 42, 43, 44

Part No. PE3C0031				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
$69.97	$71.47	$72.99	$74.61	$76.14	-	See Web

Part No. PE3C0109				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
$79.17	$80.68	$82.20	$79.20	$80.70	-	See Web

Part No. PE3W00013				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$54.10	$55.57	$57.05	$58.52	$60.00	$55.05	See Web

PE-P142LL Coax, 50 Ohm — 45

Part No. PE349				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft	820 W
12"	24"	36"	48"	60"	72"	Custom Len.
$162.10	$180.01	$197.92	$215.86	$233.77	$251.68	See Web

PE-P160LL Coax, 50 Ohm — 46

Part No. PE3C5267				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$222.74	$245.21	$267.66	$290.11	$312.56	$237.13	See Web

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm — 47

Part No. PE335				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.3" dia.	4.6 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$244.05	$272.16	$300.29	$328.42	$356.51	$262.07	See Web

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm — 48

Part No. PE33927				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W
12"	24"	36"	48"	60"	-	Custom Len.
$89.85	$98.13	$106.42	$113.12	$121.29	-	See Web

Standard Flexible Cable Assemblies

M17/60-RG142-27478 Coax, 50 Ohm — 49

Part No. PE3M0016				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.		
12"	18"	24"	30"	36"	48"	Custom Len.
$167.60	$170.55	$173.53	$176.46	$179.43	$185.35	See Web

M17/84-RG223-0XDS2 Coax, 50 Ohm — 50

Part No. PE3M0044				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.212" dia.		
12"	18"	24"	30"	36"	48"	Custom Len.
$172.26	$177.55	$182.84	$188.13	$193.43	$204.00	See Web

M17/128-RG400-27478 Coax, 50 Ohm — 51

Part No. PE3M0072				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.		
12"	18"	24"	30"	36"	48"	Custom Len.
$169.21	$172.98	$176.74	$180.50	$184.26	$191.79	See Web

RG8A/U Coax, 50 Ohm — 52

Part No. PE33615				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W
12"	24"	36"	48"	60"	72"	Custom Len.
$76.24	$79.62	$78.15	$81.27	$84.40	$93.46	See Web

RG8X Coax, 50 Ohm — 53

Part No. PE37357				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13.5 dB/100ft	60 W
12"	24"	36"	48"	60"	-	Custom Len.
$65.94	$73.78	$72.16	$75.26	$78.37	-	See Web

RG58C/U Coax, 50 Ohm — 54

Part No. PE3661				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	72"	Custom Len.
$49.20	$50.10	$51.00	$51.97	$49.68	$53.81	See Web

RG142B/U Coax, 50 Ohm — 55

Part No. PE3652				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W
12"	24"	36"	48"	60"	72"	Custom Len.
$53.63	$59.83	$66.51	$73.59	$80.40	$87.21	See Web

RG174A/U Coax, 50 Ohm — 56

Part No. PE34272				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W
12"	24"	36"	48"	60"	72"	Custom Len.
$63.76	$64.23	$64.71	$65.19	$65.67	$66.15	See Web

RG178B/U Coax, 50 Ohm — 57

Part No. PE33455				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W
12"	24"	36"	48"	60"	72"	Custom Len.
$76.58	$77.62	$78.69	$79.74	$80.81	$87.11	See Web

RG188A/U Coax, 50 Ohm — 58

Part No. PE33457				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$65.83	$68.26	$70.70	$73.15	$75.58	$78.02	See Web

RG213/U Coax, 50 Ohm — 59

Part No. PE3644				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	9 dB/100ft	190 W
12"	24"	36"	48"	60"	72"	Custom Len.
$64.16	$72.48	$74.32	$76.14	$77.97	$79.78	See Web

RG214/U Coax, 50 Ohm — 60

Part No. PE3991				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W
12"	24"	36"	48"	60"	72"	Custom Len.
$88.39	$102.25	$104.52	$111.01	$118.94	$135.39	See Web

RG223/U Coax, 50 Ohm — 61

Part No. PE3665				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W
12"	24"	36"	48"	60"	72"	Custom Len.
$52.51	$55.43	$58.86	$62.48	$61.82	$69.46	See Web

RG316/U Coax, 50 Ohm — 62

Part No. PE3989				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$72.15	$75.58	$79.02	$76.33	$79.50	$82.68	See Web

RG316-DS Coax, 50 Ohm — 63

Part No. PE34266				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$66.75	$69.95	$73.14	$76.34	$79.55	$82.73	See Web

RG393/U Coax, 50 Ohm — 64

Part No. PE3982				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W
12"	24"	36"	48"	60"	72"	Custom Len.
$96.34	$111.77	$128.54	$145.30	$162.08	$178.84	See Web

RG400/U Coax, 50 Ohm — 65

Part No. PE3666				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W
12"	24"	36"	48"	60"	72"	Custom Len.
$64.45	$72.58	$80.70	$89.32	$97.59	$105.89	See Web

PE-FF430 Coax, 50 Ohm — 66

Part No. PE3C4010				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.43" dia.		
60"	360"	-	-	-	-	Custom Len.
$1,046.18	Call	-	-	-	-	See Web

LMR-600-DB Coax, 50 Ohm — 67

Part No. PE3W02356				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$82.60	$85.85	$89.10	$92.37	$95.62	$84.69	See Web

Standard Semi-Rigid Cable Assemblies

PE-SR402AL Coax, 50 Ohm — 68

Part No. PE3W05401				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					13 dB/100ft	450 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$86.91	$97.78	$107.12	$117.84	$128.55	$93.86	See Web

RG401/U Coax, 50 Ohm — 69

Part No. PE3W05651				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	1,400 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$138.05	$163.04	$188.04	$213.04	$238.03	$154.06	See Web

Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

RG402/U Coax, 50 Ohm

Part No. PE3080				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.1 dB/100ft	450 W	70
12"	24"	36"	48"	60"	-	Custom Len.	
$94.81	$103.40	$105.49	$111.95	$119.85	-	See Web	

N MALE TO TNC MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

LMR-200 Coax, 50 Ohm

Part No. PE3W02215				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10.5 dB/100ft		71
12"	24"	36"	48"	60"	50CM	Custom Len.	
$57.62	$58.49	$59.36	$60.23	$61.10	$58.18	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5268				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			72
12"	24"	36"	48"	60"	50CM	Custom Len.	
$286.46	$308.91	$331.37	$353.83	$376.28	$300.85	See Web	

N MALE TO TNC FEMALE

Standard Flexible Cable Assemblies

PE-FF430 Coax, 50 Ohm

Part No. PE3C4011				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			73
60"	-	-	-	-	-	Custom Len.	
$1,046.18	-	-	-	-	-	See Web	

N MALE TO TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C2276				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		74
12"	24"	36"	48"	60"	50CM	Custom Len.	
$199.27	$216.88	$234.49	$252.08	$269.68	$210.56	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5269				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			75
12"	24"	36"	48"	60"	50CM	Custom Len.	
$251.25	$273.71	$296.15	$318.61	$341.07	$265.63	See Web	

Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE3W07264				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	76
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.92	$78.30	$86.67	$95.06	$103.44	$75.29	See Web	

N MALE TO REVERSE POLARITY TNC MALE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE36362				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	77
12"	24"	36"	48"	60"	-	Custom Len.	
$43.84	$44.63	$45.43	$46.20	$47.01	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE34966				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	78
12"	24"	36"	48"	60"	-	Custom Len.	
$67.96	$69.39	$75.30	$72.30	$73.75	-	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE34554				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	79
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.27	$57.90	$54.40	$55.20	$56.01	$56.83	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE34573				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	80
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.18	$60.00	$66.28	$72.60	$78.90	$85.21	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE35241				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	81
12"	24"	36"	48"	60"	72"	Custom Len.	
$79.95	$80.98	$82.05	$83.12	$84.16	$85.22	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE35243				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	82
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.64	$66.01	$68.34	$70.69	$73.07	$75.38	See Web	

RG223/U Coax, 50 Ohm

Part No. PE35245				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	83
12"	24"	36"	48"	60"	72"	Custom Len.	
$47.26	$50.45	$56.48	$56.46	$59.62	$62.85	See Web	

RG316/U Coax, 50 Ohm

Part No. PE35247				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	84
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.52	$71.70	$74.88	$78.05	$81.21	$84.40	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34626				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	85
12"	24"	36"	48"	60"	-	Custom Len.	
$61.38	$75.64	$83.78	$92.38	$100.66	-	See Web	

N MALE TO REVERSE POLARITY TNC MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE36283				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	86
12"	24"	36"	48"	60"	-	Custom Len.	
$74.33	$82.00	$89.64	$103.65	$104.97	-	See Web	

N MALE TO UMCX PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38813				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	87
3"	6"	9"	12"	18"	24"	Custom Len.	
$78.59	$78.59	$78.59	$83.31	$83.89	$79.64	See Web	

N MALE TO NEX10 MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6256				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	88
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.18	$72.31	$78.45	$84.58	$90.71	$70.09	See Web	

SPO-250 Coax, 50 Ohm

Part No. PE3C6347				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			89
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.70	$61.99	$64.26	$66.54	$68.83	$61.17	See Web	

SPF-250 Coax, 50 Ohm

Part No. PE3C6362				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.			90
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.42	$63.44	$66.46	$69.47	$72.48	$62.36	See Web	

N MALE RIGHT ANGLE TO BNC MALE

Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE3W06095				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	91
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.70	$77.06	$85.43	$93.80	$102.18	$74.06	See Web	

N MALE RIGHT ANGLE TO BNC MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

LMR-240-UF Coax, 50 Ohm

Part No. PE3C1316				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft		92
12"	24"	36"	48"	60"	50CM	Custom Len.	
$106.14	$107.57	$106.78	$108.18	$109.58	$106.35	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE3W00447				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	93
12"	24"	36"	48"	60"	50CM	Custom Len.	
$88.14	$96.50	$104.88	$111.69	$119.95	$93.51	See Web	

N MALE RIGHT ANGLE TO N MALE

Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3C0120				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		94
12"	24"	36"	48"	60"	-	Custom Len.	
$55.03	$53.21	$56.66	$54.36	$55.18	-	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4139				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			95
12"	24"	36"	48"	60"	50CM	Custom Len.	
$99.52	$105.65	$110.24	$116.29	$122.34	$103.45	See Web	

N MALE RIGHT ANGLE TO N MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE36910				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	96
12"	24"	36"	48"	60"	-	Custom Len.	
$72.22	$78.86	$79.71	$74.59	$75.36	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE38699				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	97
36"	48"	60"	72"	120"	-	Custom Len.	
$94.08	$95.14	$96.21	$98.03	$108.83	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE38194				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	98
36"	48"	60"	72"	120"	-	Custom Len.	
$124.72	$126.41	$128.05	$126.46	$147.28	-	See Web	

LMR-400 Coax, 50 Ohm

Part No. PE3C0107				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		99
12"	24"	36"	48"	60"	-	Custom Len.	
$90.94	$89.82	$93.99	$95.58	$94.33	-	See Web	

LMR-195 Coax, 50 Ohm

Part No. PE3C0119				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		1
12"	24"	36"	48"	60"	-	Custom Len.	
$56.27	$57.10	$57.93	$57.10	$57.93	-	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE3C0967				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		2
12"	24"	36"	48"	60"	50CM	Custom Len.	
$353.28	$370.88	$388.46	$406.08	$423.68	$364.55	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5287				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			3
12"	24"	36"	48"	60"	50CM	Custom Len.	
$350.17	$372.63	$395.08	$417.54	$439.99	$364.55	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0179				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			4
12"	18"	24"	36"	48"	60"	Custom Len.	
$650.65	$659.83	$669.02	$687.41	$705.79	$724.17	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0224				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			5
8"	12"	18"	24"	30"	36"	Custom Len.	
$581.93	$587.24	$595.22	$603.18	$611.16	$619.11	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0252				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			6
12"	18"	24"	36"	48"	60"	Custom Len.	
$767.54	$782.88	$798.23	$828.92	$859.60	$890.28	See Web	

Precision Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39444				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	7
6"	9"	12"	18"	24"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39458				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	8
6"	9"	12"	18"	24"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7846				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		9
12"	50CM	24"	36"	48"	60"	Custom Len.	
$64.71	$67.09	$68.44	$72.17	$75.90	$79.62	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4145				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	10
12"	24"	36"	48"	60"	50CM	Custom Len.	
$102.60	$107.24	$113.29	$119.34	$125.39	$106.55	See Web	

Part No. PE3C6206				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	11
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.86	$69.00	$75.12	$81.26	$87.40	$66.78	See Web	

SPO-500 Coax, 50 Ohm

Part No. PE3C6373				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.53" dia.			12
12"	24"	36"	48"	60"	50CM	Custom Len.	
$50.20	$53.31	$55.91	$58.98	$62.07	$52.19	See Web	

SPF-500 Coax, 50 Ohm

Part No. PE3C6376				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.545" dia.			13
12"	24"	36"	48"	60"	50CM	Custom Len.	
$51.51	$55.42	$59.80	$64.20	$68.58	$54.35	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3233				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		14
12"	24"	36"	48"	60"	50CM	Custom Len.	
$366.99	$395.10	$423.23	$451.35	$479.47	$385.00	See Web	

Standard Formable Cable Assemblies

PE-SR401FL Coax, 50 Ohm

Part No. PE34680				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	15
12"	24"	36"	48"	60"	-	Custom Len.	
$124.78	$134.40	$151.10	$167.80	$184.51	-	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE33977				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	16
12"	24"	36"	48"	60"	-	Custom Len.	
$83.89	$92.19	$100.48	$107.25	$115.43	-	See Web	

Part No. PE39452				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	400 W	17
6"	9"	12"	18"	24"	-	Custom Len.	
$84.37	$86.52	$88.68	Call	Call	-	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39466				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	18
6"	9"	12"	18"	24"	-	Custom Len.	
$84.45	Call	$84.45	$88.61	$92.76	-	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE33974				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	19
12"	24"	36"	48"	60"	72"	Custom Len.	
$117.41	$120.74	$124.08	$122.12	$125.17	$134.40	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3698				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	20
12"	24"	36"	48"	60"	72"	Custom Len.	
$86.78	$82.68	$88.56	$84.31	$85.12	$91.34	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE34231				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	21
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.69	$78.23	$78.69	$79.20	$79.69	$80.14	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34238				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	22
12"	24"	36"	48"	60"	72"	Custom Len.	
$92.84	$86.85	$98.33	$91.73	$94.17	$96.61	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3272				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	9 dB/100ft	190 W	23
12"	24"	36"	48"	60"	72"	Custom Len.	
$116.13	$111.36	$113.16	$122.06	$116.76	$118.56	See Web	

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

See Our Website For Current Pricing & Real-Time Stock Availability!

RG214/U Coax, 50 Ohm

Part No. PE3781				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	24
12"	24"	36"	48"	60"	72"	Custom Len.	
$131.14	$147.43	$147.03	$154.96	$173.40	$182.00	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3882				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	25
12"	24"	36"	48"	60"	72"	Custom Len.	
$92.19	$88.53	$91.73	$94.92	$98.11	$101.30	See Web	

RG225/U Coax, 50 Ohm

Part No. PE34222				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	26
12"	24"	36"	48"	60"	72"	Custom Len.	
$154.63	$189.97	$225.31	$288.23	$295.96	$331.29	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34236				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	27
12"	24"	36"	48"	60"	72"	Custom Len.	
$85.36	$88.53	$91.72	$94.89	$98.06	$107.99	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3268				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	28
12"	24"	36"	48"	60"	72"	Custom Len.	
$125.57	$150.88	$168.68	$187.50	$205.62	$223.76	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3412				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	29
12"	24"	36"	48"	60"	72"	Custom Len.	
$101.33	$107.95	$115.96	$124.45	$124.49	$140.79	See Web	

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1049				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			30
12"	24"	36"	50CM	100CM	-	Custom Len.	
$116.21	$129.56	$147.24	$123.18	$152.20	-	See Web	

N MALE RIGHT ANGLE TO N FEMALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7847				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		31
12"	24"	36"	48"	60"	50CM	Custom Len.	
$61.96	$65.69	$69.42	$73.14	$76.87	$64.35	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6203				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	32
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.24	$66.37	$72.49	$78.63	$84.76	$64.16	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3115				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		33
12"	24"	36"	48"	60"	50CM	Custom Len.	
$354.16	$382.29	$410.41	$438.53	$466.65	$372.18	See Web	

Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE3W06096				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	34
12"	24"	36"	48"	60"	50CM	Custom Len.	
$77.08	$85.44	$93.81	$102.19	$109.02	$82.43	See Web	

N MALE RIGHT ANGLE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Flexible Cable Assemblies

LMR-400 Coax, 50 Ohm

Part No. PE3W03991				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		35
12"	24"	36"	48"	60"	50CM	Custom Len.	
$80.55	$81.93	$83.29	$84.67	$86.04	$81.44	See Web	

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C0673				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		36
12"	24"	36"	48"	60"	50CM	Custom Len.	
$285.96	$303.05	$320.12	$337.21	$354.30	$296.91	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5286				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			37
12"	24"	36"	48"	60"	50CM	Custom Len.	
$314.95	$337.42	$359.87	$382.32	$404.78	$329.33	See Web	

LMR-240-UF Coax, 50 Ohm

Part No. PE3W06441				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft		38
12"	24"	36"	48"	60"	50CM	Custom Len.	
$85.85	$87.32	$88.81	$90.29	$91.78	$86.80	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7848				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		39
12"	24"	36"	48"	60"	50CM	Custom Len.	
$61.96	$65.69	$69.42	$73.14	$76.87	$64.35	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6204				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	40
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.24	$66.37	$72.49	$78.63	$84.76	$64.16	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C2953				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		41
12"	24"	36"	48"	60"	50CM	Custom Len.	
$379.75	$407.05	$434.37	$461.65	$489.27	$397.25	See Web	

Standard Formable Cable Assemblies

PE-SR401FL Coax, 50 Ohm

Part No. PE39082				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	42
12"	24"	36"	48"	60"	-	Custom Len.	
$107.65	$121.56	$137.01	$152.43	$167.89	-	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE38670				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	43
12"	24"	36"	48"	60"	-	Custom Len.	
$94.03	$96.63	$104.49	$110.79	$118.52	-	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE34216				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	44
12"	24"	36"	48"	60"	72"	Custom Len.	
$99.22	$102.18	$105.21	$106.75	$109.68	$112.67	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3407				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	45
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.32	$79.20	$74.14	$74.95	$75.77	$76.57	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE33021				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		46
12"	24"	36"	48"	60"	72"	Custom Len.	
$80.11	$81.87	$88.19	$94.48	$107.37	$107.09	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE34229				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	47
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.42	$78.89	$79.43	$79.87	$80.40	$80.86	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34218				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	48
12"	24"	36"	48"	60"	72"	Custom Len.	
$80.28	$82.65	$84.96	$87.33	$89.70	$92.01	See Web	

RG213/U Coax, 50 Ohm

Part No. PE33545				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	49
12"	24"	36"	48"	60"	72"	Custom Len.	
$103.92	$105.75	$107.56	$107.87	$109.68	$111.48	See Web	

RG214/U Coax, 50 Ohm

Part No. PE33178				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	50
12"	24"	36"	48"	60"	72"	Custom Len.	
$96.63	$104.75	$111.30	$119.31	$127.32	$135.30	See Web	

RG223/U Coax, 50 Ohm

Part No. PE33536				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	51
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.39	$75.93	$74.78	$78.01	$81.19	$89.96	See Web	

RG225/U Coax, 50 Ohm

Part No. PE34221				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	52
12"	24"	36"	48"	60"	72"	Custom Len.	
$122.63	$157.97	$193.28	$228.61	$263.94	$299.26	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34214				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	53
12"	24"	36"	48"	60"	72"	Custom Len.	
$81.26	$84.57	$87.84	$91.16	$94.45	$97.77	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

RG316-DS Coax, 50 Ohm

Part No. PE34227				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	26.1 dB/100ft	160 W	54
12"	24"	36"	48"	60"	72"	Custom Len.	
$86.29	$89.46	$92.66	$95.87	$99.07	$102.27	See Web	

RG393/U Coax, 50 Ohm

Part No. PE33532				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	55
12"	24"	36"	48"	60"	72"	Custom Len.	
$102.44	$117.78	$134.56	$151.32	$168.09	$184.86	See Web	

RG400/U Coax, 50 Ohm

Part No. PE33528				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	56
12"	24"	36"	48"	60"	72"	Custom Len.	
$84.26	$91.92	$103.89	$110.94	$113.31	$120.86	See Web	

N MALE RIGHT ANGLE TO SMA MALE

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5279				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			57
12"	24"	36"	48"	60"	50CM	Custom Len.	
$286.46	$308.91	$331.37	$353.83	$376.28	$300.85	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6209				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	58
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.98	$61.12	$67.26	$73.38	$79.51	$58.90	See Web	

N MALE RIGHT ANGLE TO SMA MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5281				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			59
12"	24"	36"	48"	60"	50CM	Custom Len.	
$326.69	$349.15	$371.60	$394.05	$416.52	$341.08	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6211				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	60
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.24	$66.37	$72.49	$78.63	$84.76	$64.16	See Web	

N MALE RIGHT ANGLE TO SMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5280				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			61
12"	24"	36"	48"	60"	50CM	Custom Len.	
$304.90	$327.35	$349.80	$372.27	$394.73	$319.28	See Web	

N MALE RIGHT ANGLE TO TNC MALE

Flexible Cable Assemblies

LMR-600-DB Coax, 50 Ohm

Part No. PE3C4750				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft		62
12"	24"	36"	48"	60"	50CM	Custom Len.	
$93.49	$91.45	$94.71	$97.96	$101.22	$90.28	See Web	

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5282				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			63
12"	24"	36"	48"	60"	50CM	Custom Len.	
$286.46	$308.91	$331.37	$353.83	$376.28	$300.85	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3243				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		64
12"	24"	36"	48"	60"	50CM	Custom Len.	
$410.04	$437.36	$464.69	$492.00	$519.34	$427.53	See Web	

N MALE RIGHT ANGLE TO TNC MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3W00020				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		65
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.74	$64.52	$65.32	$66.13	$66.92	$64.24	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE3C1271				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		66
12"	24"	36"	48"	60"	50CM	Custom Len.	
$374.47	$370.88	$388.46	$406.08	$423.68	$364.55	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5284				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			67
12"	24"	36"	48"	60"	50CM	Custom Len.	
$350.17	$372.63	$395.08	$417.54	$439.99	$364.55	See Web	

N MALE RIGHT ANGLE TO TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5283				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			68
12"	24"	36"	48"	60"	50CM	Custom Len.	
$314.95	$337.42	$359.87	$382.32	$404.78	$329.33	See Web	

N MALE RIGHT ANGLE TO UHF MALE

Standard Flexible Cable Assemblies

RG214/U Coax, 50 Ohm

Part No. PE38204				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	69
12"	24"	36"	48"	60"	-	Custom Len.	
$106.88	$113.82	$122.26	$131.19	$131.20	-	See Web	

N MALE RIGHT ANGLE TO NEX10 MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6257				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	70
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.80	$74.94	$81.07	$87.20	$93.34	$72.72	See Web	

N FEMALE TO N FEMALE

Standard Flexible Cable Assemblies

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0011				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			71
12"	18"	24"	30"	36"	48"	Custom Len.	
$185.55	$188.50	$191.46	$194.41	$197.37	$203.29	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0039				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			72
12"	18"	24"	30"	36"	48"	Custom Len.	
$190.21	$195.50	$200.79	$206.07	$211.36	$221.94	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0067				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			73
12"	18"	24"	30"	36"	48"	Custom Len.	
$187.16	$190.92	$194.69	$198.45	$202.21	$209.74	See Web	

N FEMALE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0012				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			74
12"	18"	24"	30"	36"	48"	Custom Len.	
$189.71	$192.66	$195.62	$198.57	$201.55	$207.46	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0040				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			75
12"	18"	24"	30"	36"	48"	Custom Len.	
$194.38	$199.66	$204.96	$210.25	$215.53	$226.12	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0068				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			76
12"	18"	24"	30"	36"	48"	Custom Len.	
$191.32	$195.08	$198.85	$202.61	$206.37	$213.91	See Web	

N FEMALE TO SMA MALE

Standard Flexible Cable Assemblies

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0017				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			77
12"	18"	24"	30"	36"	48"	Custom Len.	
$211.28	$214.24	$217.20	$220.15	$223.11	$229.03	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0045				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			78
12"	18"	24"	30"	36"	48"	Custom Len.	
$215.96	$221.24	$226.53	$231.81	$237.11	$247.68	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0073				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			79
12"	18"	24"	30"	36"	48"	Custom Len.	
$212.90	$216.66	$220.42	$224.19	$227.95	$235.47	See Web	

N FEMALE TO SMA MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0018				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			80
12"	18"	24"	30"	36"	48"	Custom Len.	
$250.41	$253.36	$256.32	$259.28	$262.24	$268.15	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0046				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			81
12"	18"	24"	30"	36"	48"	Custom Len.	
$255.07	$260.35	$265.66	$270.93	$276.22	$286.81	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0074				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			82
12"	18"	24"	30"	36"	48"	Custom Len.	
$252.03	$255.76	$259.55	$263.30	$267.08	$274.59	See Web	

N FEMALE TO TNC MALE

Standard Flexible Cable Assemblies

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0019				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			83
12"	18"	24"	30"	36"	48"	Custom Len.	
$177.99	$180.94	$183.91	$186.86	$189.82	$195.73	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0047				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			84
12"	18"	24"	30"	36"	48"	Custom Len.	
$182.65	$187.95	$193.23	$198.51	$203.81	$214.38	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0075				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			85
12"	18"	24"	30"	36"	48"	Custom Len.	
$179.61	$183.37	$187.13	$190.88	$194.66	$202.17	See Web	

N FEMALE TO 7/16 DIN MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C4133				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.		650 W	86
12"	24"	36"	48"	60"	50CM	Custom Len.	
$101.58	$107.71	$112.27	$118.32	$124.37	$105.50	See Web	

N FEMALE TO N MALE

Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39460				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	87
6"	9"	12"	18"	24"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39468				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	88
6"	9"	12"	18"	24"	-	Custom Len.	
Call	$93.79	$96.03	Call	$98.88	-	See Web	

N FEMALE TO N FEMALE

Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3W07489				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			89
12"	24"	36"	48"	60"	50CM	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

Low Loss Flexible Cable Assemblies

LMR-600-DB Coax, 50 Ohm

Part No. PE3W05453				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft		90
12"	18"	24"	36"	48"	60"	Custom Len.	
$80.69	$79.09	$80.52	$83.37	$86.22	$89.06	See Web	

Low PIM Corrugated Cable Assemblies

SPO-375 Coax, 50 Ohm

Part No. PE3C6378				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			91
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.36	$86.06	$105.77	$123.73	$143.16	$78.99	See Web	

SPF-375 Coax, 50 Ohm

Part No. PE3C6379				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.435" dia.			92
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.36	$86.06	$105.77	$123.73	$143.16	$78.99	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3234				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		93
12"	24"	36"	48"	60"	50CM	Custom Len.	
$291.93	$319.23	$346.53	$373.83	$401.14	$309.43	See Web	

Standard Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C0126				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		94
12"	24"	36"	48"	60"	-	Custom Len.	
$153.33	$142.41	$160.07	$148.46	$151.47	-	See Web	

N FEMALE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3247				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		95
12"	24"	36"	48"	60"	50CM	Custom Len.	
$347.77	$375.10	$402.42	$429.74	$457.06	$365.27	See Web	

Standard Flexible Cable Assemblies

PE-P195 Coax, 50 Ohm

Part No. PE3W02976				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	96
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.37	$69.82	$81.27	$92.73	$104.19	$65.70	See Web	

N FEMALE TO QN MALE

Low Loss Flexible Cable Assemblies

Continued on Next Page

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-C195 Coax, 50 Ohm

Part No. PE38457				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	97
12"	24"	36"	48"	60"	72"	Custom Len.	
$71.32	$72.11	$72.89	$73.66	$74.45	$75.25	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE38456				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	98
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.57	$71.43	$72.22	$73.01	$73.80	$74.61	See Web	

RG213/U Coax, 50 Ohm

Part No. PE38454				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	99
12"	24"	36"	48"	60"	72"	Custom Len.	
$112.47	$114.29	$116.12	$117.93	$119.75	$121.51	See Web	

RG223/U Coax, 50 Ohm

Part No. PE38455				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	1
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.77	$72.95	$76.18	$79.34	$82.58	$85.81	See Web	

N FEMALE TO QN MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38494				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	2
12"	24"	36"	48"	60"	72"	Custom Len.	
$71.71	$72.41	$73.21	$73.93	$74.73	$83.25	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE38493				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	3
12"	24"	36"	48"	60"	72"	Custom Len.	
$84.96	$85.76	$86.53	$87.33	$88.20	$88.98	See Web	

RG213/U Coax, 50 Ohm

Part No. PE38495				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	4
12"	24"	36"	48"	60"	72"	Custom Len.	
$99.13	$101.00	$102.83	$104.69	$106.53	$106.82	See Web	

RG223/U Coax, 50 Ohm

Part No. PE38496				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	5
12"	24"	36"	48"	60"	72"	Custom Len.	
$74.73	$77.96	$81.13	$84.36	$87.53	$90.77	See Web	

N FEMALE TO SMA MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6215				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	6
12"	24"	36"	48"	60"	50CM	Custom Len.	
$52.84	$58.49	$64.62	$70.76	$76.88	$56.27	See Web	

N FEMALE TO SMA MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

LMR-240-UF Coax, 50 Ohm

Part No. PE3W04423				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft		7
12"	24"	36"	48"	60"	50CM	Custom Len.	
$57.80	$59.28	$60.75	$62.23	$63.74	$58.76	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6217				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	8
12"	24"	36"	48"	60"	50CM	Custom Len.	
$57.61	$63.75	$69.88	$76.00	$82.14	$61.52	See Web	

N FEMALE TO TNC MALE

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3244				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		9
12"	24"	36"	48"	60"	50CM	Custom Len.	
$265.55	$292.88	$320.21	$347.53	$374.86	$283.05	See Web	

N FEMALE TO NEX10 MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6254				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	10
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.18	$72.31	$78.45	$84.58	$90.71	$70.09	See Web	

N FEMALE BULKHEAD TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0013				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			11
12"	18"	24"	30"	36"	48"	Custom Len.	
$193.88	$196.83	$199.80	$202.75	$205.71	$211.63	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0041				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			12
12"	18"	24"	30"	36"	48"	Custom Len.	
$198.54	$203.84	$209.13	$214.40	$219.70	$230.28	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0069				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			13
12"	18"	24"	30"	36"	48"	Custom Len.	
$195.50	$199.26	$203.03	$206.79	$210.54	$218.07	See Web	

N FEMALE BULKHEAD TO SMA MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0020				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			14
12"	18"	24"	30"	36"	48"	Custom Len.	
$215.45	$218.40	$221.37	$224.33	$227.29	$233.20	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0048				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			15
12"	18"	24"	30"	36"	48"	Custom Len.	
$220.12	$225.40	$230.71	$235.98	$241.27	$251.86	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0076				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			16
12"	18"	24"	30"	36"	48"	Custom Len.	
$217.06	$220.83	$224.59	$228.36	$232.12	$239.64	See Web	

N FEMALE BULKHEAD TO SMA MALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0021				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			17
12"	18"	24"	30"	36"	48"	Custom Len.	
$254.57	$257.53	$260.49	$263.44	$266.40	$272.33	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0049				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			18
12"	18"	24"	30"	36"	48"	Custom Len.	
$259.25	$264.53	$269.81	$275.09	$280.40	$290.97	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0077				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			19
12"	18"	24"	30"	36"	48"	Custom Len.	
$256.19	$259.94	$263.71	$267.47	$271.24	$278.76	See Web	

N FEMALE BULKHEAD TO TNC MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0022				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			20
12"	18"	24"	30"	36"	48"	Custom Len.	
$200.37	$185.11	$188.07	$191.02	$193.99	$199.89	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0050				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			21
12"	18"	24"	30"	36"	48"	Custom Len.	
$186.83	$192.10	$197.39	$202.69	$207.98	$218.55	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0078				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			22
12"	18"	24"	30"	36"	48"	Custom Len.	
$183.77	$187.53	$191.29	$195.05	$198.82	$206.34	See Web	

N FEMALE BULKHEAD TO MCX PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Precision Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39449				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	23
6"	9"	12"	18"	24"	-	Custom Len.	
$56.16	Call	Call	$68.47	Call	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39463				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	24
6"	9"	12"	18"	24"	36"	Custom Len.	
$54.17	$54.17	Call	$58.42	$62.69	Call	See Web	

N FEMALE BULKHEAD TO MMCX PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Precision Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39450				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	25
6"	9"	12"	18"	24"	-	Custom Len.	
$57.12	Call	$61.68	$63.00	$68.87	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39464				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	26
6"	9"	12"	18"	24"	30"	Custom Len.	
$54.60	$56.88	$54.77	$59.04	$63.29	Call	See Web	

N FEMALE BULKHEAD TO N MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1050				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			27
12"	24"	36"	50CM	100CM	-	Custom Len.	
$101.54	$119.07	$138.03	$112.27	$143.32	-	See Web	

N FEMALE BULKHEAD TO N MALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0178				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			28
12"	18"	24"	36"	48"	60"	Custom Len.	
$620.47	$629.66	$638.86	$657.24	$675.62	$694.01	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0223				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			29
8"	12"	18"	24"	30"	36"	Custom Len.	
$586.19	$591.52	$599.47	$607.45	$615.42	$623.38	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0251				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			30
12"	18"	24"	36"	48"	60"	Custom Len.	
$692.44	$707.78	$723.13	$753.81	$784.49	$815.18	See Web	

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3W03365				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	31
12"	24"	36"	48"	60"	50CM	Custom Len.	
$82.80	$92.56	$102.32	$110.54	$120.17	$89.04	See Web	

N FEMALE BULKHEAD TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C1000				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		32
12"	24"	36"	48"	60"	50CM	Custom Len.	
$240.61	$257.70	$274.79	$291.87	$308.95	$251.57	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5256				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			33
12"	24"	36"	48"	60"	50CM	Custom Len.	
$279.74	$302.20	$324.65	$347.11	$369.56	$294.13	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0177				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			34
12"	18"	24"	36"	48"	60"	Custom Len.	
$590.30	$599.49	$608.67	$627.07	$645.45	$663.83	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0222				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			35
8"	12"	18"	24"	30"	36"	Custom Len.	
$590.46	$595.79	$603.74	$611.72	$619.68	$627.66	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0250				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			36
12"	18"	24"	36"	48"	60"	Custom Len.	
$617.34	$632.69	$648.04	$678.72	$709.40	$740.08	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3232				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		37
12"	24"	36"	48"	60"	50CM	Custom Len.	
$283.23	$310.53	$337.82	$365.13	$392.44	$300.72	See Web	

N FEMALE BULKHEAD TO QMA MALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4238				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	38
12"	24"	36"	48"	60"	50CM	Custom Len.	
$71.57	$74.90	$78.24	$81.57	$84.90	$73.70	See Web	

N FEMALE BULKHEAD TO SMA MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5274				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			39
12"	24"	36"	48"	60"	50CM	Custom Len.	
$251.25	$273.71	$296.15	$318.61	$341.07	$265.63	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6214				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	40
12"	24"	36"	48"	60"	50CM	Custom Len.	
$52.84	$58.49	$64.62	$70.76	$76.88	$56.27	See Web	

N FEMALE BULKHEAD TO SMA MALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Flexible Cable Assemblies

PE-P195 Coax, 50 Ohm

Part No. PE3W06405				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	41
12"	24"	36"	48"	60"	50CM	Custom Len.	
$56.38	$67.84	$79.29	$90.75	$102.21	$63.72	See Web	

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5276				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			42
12"	24"	36"	48"	60"	50CM	Custom Len.	
$291.47	$313.95	$336.40	$358.84	$381.31	$305.86	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6216				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	43
12"	24"	36"	48"	60"	50CM	Custom Len.	
$57.61	$63.75	$69.88	$76.00	$82.14	$61.52	See Web	

N FEMALE BULKHEAD TO SMA FEMALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Flexible Cable Assemblies

LMR-400-UF Coax, 50 Ohm

Part No. PE3W05630				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	5 dB/100ft		44
12"	24"	36"	48"	60"	50CM	Custom Len.	
$93.69	$96.58	$99.46	$102.35	$105.24	$95.54	See Web	

N FEMALE BULKHEAD TO SMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5278				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			45
12"	24"	36"	48"	60"	50CM	Custom Len.	
$269.68	$269.68	$269.68	$269.68	$269.68	$269.68	See Web	

N FEMALE BULKHEAD TO REVERSE POLARITY SMA MALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE3C5030				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	46
12"	24"	36"	48"	60"	50CM	Custom Len.	
$91.96	$94.63	$102.53	$108.89	$116.68	$91.80	See Web	

N FEMALE BULKHEAD TO SMP FEMALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3W04763				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	47
12"	24"	36"	48"	60"	50CM	Custom Len.	
$80.72	$81.84	$82.97	$84.10	$85.24	$81.45	See Web	

N FEMALE BULKHEAD TO TNC MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C1110				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		48
12"	24"	36"	48"	60"	50CM	Custom Len.	
$203.47	$220.58	$238.85	$254.73	$271.82	$214.42	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5270				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			49
12"	24"	36"	48"	60"	50CM	Custom Len.	
$251.25	$273.71	$296.15	$318.61	$341.07	$265.63	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C1084				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		50
12"	24"	36"	48"	60"	50CM	Custom Len.	
$275.03	$302.33	$329.63	$356.94	$384.23	$292.53	See Web	

N FEMALE BULKHEAD TO TNC MALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

LMR-240 Coax, 50 Ohm

Part No. PE3W00415				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		51
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.02	$60.05	$61.10	$62.13	$63.16	$59.69	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5271				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			52
12"	24"	36"	48"	60"	50CM	Custom Len.	
$314.95	$337.42	$359.87	$382.32	$404.78	$329.33	See Web	

N FEMALE BULKHEAD TO TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5272				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			53
12"	24"	36"	48"	60"	50CM	Custom Len.	
$279.74	$302.20	$324.65	$347.11	$369.56	$294.13	See Web	

N FEMALE BULKHEAD TO HMCX32 1.2 PLUG

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1015				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			54
3"	6"	12"	-	-	-	Custom Len.	
Call	$23.27	Call	-	-	-	See Web	

N FEMALE BULKHEAD TO UMCX 2.1 PLUG

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1013				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			55
3"	6"	12"	-	-	-	Custom Len.	
Call	$23.27	$23.27	-	-	-	See Web	

N FEMALE BULKHEAD TO UMCX 2.5 PLUG

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3CA1011				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.07" dia.			56
3"	6"	9"	12"	-	-	Custom Len.	
Call	$21.64	$20.19	$21.63	-	-	See Web	

RG178-DS Coax, 50 Ohm

Part No. PE3CA1012				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.086" dia.			57
3"	6"	9"	12"	-	-	Custom Len.	
Call	$20.19	$24.56	$21.63	-	-	See Web	

PE-81mm Coax, 50 Ohm

Part No. PE3CA1008				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			58
3"	6"	12"	-	-	-	Custom Len.	
Call	$20.19	Call	-	-	-	See Web	

PE-113mm Coax, 50 Ohm

Part No. PE3CA1009				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.044" dia.			59
3"	6"	12"	-	-	-	Custom Len.	
Call	$20.19	$23.27	-	-	-	See Web	

PE-137mm Coax, 50 Ohm

Part No. PE3CA1010				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.053" dia.			60
3"	6"	12"	20CM	-	-	Custom Len.	
Call	$20.19	$23.42	Call	-	-	See Web	

N FEMALE BULKHEAD TO WMCX 1.6 PLUG

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1014				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			61
3"	6"	12"	-	-	-	Custom Len.	
Call	Call	$22.47	-	-	-	See Web	

N FEMALE BULKHEAD TO NEX10 MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6255				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$66.18	$72.31	$78.45	$84.58	$90.71	$70.09	See Web

62

N FEMALE 4 HOLE FLANGE TO MMCX PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C0063				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
$61.83	$58.00	$58.79	$59.55	$60.31	-	See Web

63

N FEMALE 4 HOLE FLANGE TO N MALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Semi-Rigid Cable Assemblies

RG402/U Coax, 50 Ohm

Part No. PE3W07619				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					11.1 dB/100ft	450 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$94.42	$102.78	$109.58	$117.83	$126.07	$99.78	See Web

64

NMO MOUNT SEXLESS TO TNC MALE

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37848				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
60"	120"	180"	-	-	-	Custom Len.
$51.81	$51.93	$55.48	-	-	-	See Web

65

QMA MALE TO QMA MALE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38272				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W
12"	24"	36"	48"	60"	72"	Custom Len.
$54.54	$55.33	$59.53	$56.90	$57.69	$62.19	See Web

66

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7870				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$54.07	$57.80	$61.52	$65.25	$68.97	$56.46	See Web

67

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5869				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$78.94	$85.08	$91.21	$97.35	$103.48	$82.87	See Web

68

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE38271				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	72"	Custom Len.
$63.20	$63.99	$64.82	$65.63	$66.44	$67.26	See Web

69

RG316/U Coax, 50 Ohm

Part No. PE38270				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$67.30	$70.47	$78.21	$76.80	$85.34	$83.18	See Web

70

RG316-DS Coax, 50 Ohm

Part No. PE38161				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$106.07	$107.77	$110.91	$114.10	$117.29	$120.47	See Web

71

QMA MALE TO QMA MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7871				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$58.29	$62.02	$65.74	$69.47	$73.20	$60.68	See Web

72

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5875				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$81.34	$87.47	$93.61	$99.73	$105.87	$85.26	See Web

73

QMA MALE TO QMA FEMALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7872				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$54.40	$57.62	$61.35	$65.07	$68.80	$56.28	See Web

74

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5863				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$74.99	$81.12	$87.26	$93.39	$99.53	$78.92	See Web

75

QMA MALE TO QMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7873				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$43.86	$47.62	$51.38	$54.63	$58.36	$46.26	See Web

76

QMA MALE TO SMA MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5870				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$71.00	$77.14	$83.27	$89.41	$95.54	$74.94	See Web

77

QMA MALE TO SMA MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5893				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$72.60	$78.74	$84.87	$91.01	$97.15	$76.53	See Web

78

QMA MALE TO SMA FEMALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5882				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$71.80	$77.94	$84.07	$90.21	$96.34	$75.73	See Web

79

QMA MALE RIGHT ANGLE TO QMA MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7874				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$62.52	$66.24	$69.97	$73.69	$77.42	$64.90	See Web

80

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5877				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.28" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$83.73	$89.86	$96.00	$102.13	$106.76	$87.65	See Web

81

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C7587				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
Call	Call	Call	Call	Call	Call	See Web

82

See Our Website For Current Pricing & Real-Time Stock Availability!

QMA MALE RIGHT ANGLE TO QMA FEMALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7875				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		83
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.12	$61.85	$65.57	$69.30	$73.02	$60.51	See Web	

QMA MALE RIGHT ANGLE TO QMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7876				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		84
12"	24"	36"	48"	60"	50CM	Custom Len.	
$48.12	$51.88	$55.13	$58.85	$62.58	$50.52	See Web	

QMA MALE RIGHT ANGLE TO SMA MALE

Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3W06662				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		85
12"	24"	36"	48"	60"	50CM	Custom Len.	
$61.76	$62.46	$63.17	$63.88	$64.58	$62.19	See Web	

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5876				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			86
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.40	$79.53	$85.66	$91.76	$97.93	$77.32	See Web	

QMA FEMALE TO SMA MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5864				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			87
12"	24"	36"	48"	60"	50CM	Custom Len.	
$67.05	$73.19	$79.32	$85.45	$91.59	$70.98	See Web	

QN MALE TO QN MALE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38449				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	88
12"	24"	36"	48"	60"	72"	Custom Len.	
$86.53	$87.27	$87.99	$88.78	$89.52	$90.29	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE38448				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	89
12"	24"	36"	48"	60"	72"	Custom Len.	
$87.60	$88.45	$89.25	$90.02	$90.82	$91.61	See Web	

RG213/U Coax, 50 Ohm

Part No. PE38446				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	90
12"	24"	36"	48"	60"	72"	Custom Len.	
$164.65	$166.48	$168.22	$170.06	$171.87	$173.71	See Web	

RG223/U Coax, 50 Ohm

Part No. PE38447				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	91
12"	24"	36"	48"	60"	72"	Custom Len.	
$88.98	$92.15	$95.38	$98.61	$101.77	$105.02	See Web	

QN MALE TO QN MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38486				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	92
12"	24"	36"	48"	60"	72"	Custom Len.	
$88.72	$89.45	$90.24	$90.96	$91.76	$92.49	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE38485				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	93
12"	24"	36"	48"	60"	72"	Custom Len.	
$106.59	$107.40	$108.20	$108.98	$109.79	$110.58	See Web	

RG213/U Coax, 50 Ohm

Part No. PE38487				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	94
12"	24"	36"	48"	60"	72"	Custom Len.	
$149.95	$151.78	$153.51	$155.34	$157.17	$158.98	See Web	

RG223/U Coax, 50 Ohm

Part No. PE38488				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	95
12"	24"	36"	48"	60"	72"	Custom Len.	
$93.94	$97.17	$100.32	$103.57	$106.80	$108.42	See Web	

QN MALE RIGHT ANGLE TO N FEMALE

Flexible Cable Assemblies

LMR-400 Coax, 50 Ohm

Part No. PE3W04619				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		96
12"	24"	36"	48"	60"	50CM	Custom Len.	
$96.31	$97.67	$99.05	$100.42	$101.78	$97.19	See Web	

SC MALE TO SC MALE

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE34443				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	97
12"	24"	36"	48"	60"	72"	Custom Len.	
$166.26	$179.56	$172.40	$186.41	$178.54	$181.61	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3104				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	98
12"	24"	36"	48"	60"	72"	Custom Len.	
$258.68	$259.50	$260.30	$261.09	$261.87	$262.64	See Web	

RG141A/U Coax, 50 Ohm

Part No. PE34439				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W	99
12"	24"	36"	48"	60"	72"	Custom Len.	
$271.19	$277.99	$284.76	$291.54	$298.31	$305.07	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3334				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	1
12"	24"	36"	48"	60"	72"	Custom Len.	
$257.45	$263.43	$269.42	$275.47	$281.43	$287.50	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3395				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	2
12"	24"	36"	48"	60"	72"	Custom Len.	
$155.67	$157.50	$159.33	$161.15	$162.90	$164.72	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3409				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	3
12"	24"	36"	48"	60"	72"	Custom Len.	
$171.58	$179.54	$187.47	$195.42	$203.36	$211.28	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3348				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	4
12"	24"	36"	48"	60"	72"	Custom Len.	
$254.57	$257.70	$260.90	$264.08	$267.20	$270.39	See Web	

RG225/U Coax, 50 Ohm

Part No. PE34447				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	5
12"	24"	36"	48"	60"	72"	Custom Len.	
$212.56	$236.96	$273.38	$309.82	$346.24	$382.67	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3416				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W	6
12"	24"	36"	48"	60"	72"	Custom Len.	
$181.02	$209.67	$227.45	$231.33	$248.10	$264.86	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

RG400/U Coax, 50 Ohm

Part No. PE34453				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	7
12"	24"	36"	48"	60"	72"	Custom Len.	
$265.49	$273.13	$280.74	$288.34	$295.96	$303.57	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE34441				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	8
12"	24"	36"	48"	60"	72"	Custom Len.	
$258.87	$259.84	$260.84	$261.80	$262.78	$263.75	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE34449				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	9
12"	24"	36"	48"	60"	72"	Custom Len.	
$259.33	$260.75	$262.21	$263.61	$265.06	$266.49	See Web	

SHV PLUG TO SHV PLUG

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE33068				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	10
12"	24"	36"	48"	60"	72"	Custom Len.	
$113.80	$110.43	$113.50	$116.58	$119.65	$130.79	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3815				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	11
12"	24"	36"	48"	60"	72"	Custom Len.	
$111.95	$112.83	$113.72	$114.65	$115.54	$116.44	See Web	

RG141A/U Coax, 50 Ohm

Part No. PE34428				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W	12
12"	24"	36"	48"	60"	72"	Custom Len.	
$132.78	$132.26	$147.74	$146.25	$163.29	$170.92	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3843				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	13
12"	24"	36"	48"	60"	72"	Custom Len.	
$105.94	$106.24	$117.64	$117.21	$131.35	$138.06	See Web	
Part No. PE3W03503				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft	600 W	14
12"	24"	36"	48"	60"	50CM	Custom Len.	
$77.25	$83.73	$90.21	$96.70	$103.18	$81.39	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE33706				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	15
12"	24"	36"	48"	60"	72"	Custom Len.	
$125.72	$119.07	$126.97	$127.63	$128.26	$120.96	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34430				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	16
12"	24"	36"	48"	60"	72"	Custom Len.	
$127.79	$130.50	$125.38	$127.78	$130.19	$141.58	See Web	

RG213/U Coax, 50 Ohm

Part No. PE35384				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	9 dB/100ft	190 W	17
12"	24"	36"	48"	60"	-	Custom Len.	
$107.47	$109.41	$111.34	$113.41	$115.37	-	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3117				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	18
12"	24"	36"	48"	60"	72"	Custom Len.	
$121.48	$129.91	$138.35	$138.42	$155.88	$164.47	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3992				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	19
12"	24"	36"	48"	60"	72"	Custom Len.	
$100.75	$104.18	$107.61	$109.69	$108.11	$116.57	See Web	

RG225/U Coax, 50 Ohm

Part No. PE34421				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	20
12"	24"	36"	48"	60"	72"	Custom Len.	
$143.57	$182.19	$220.81	$241.44	$301.06	$312.11	See Web	

RG303/U Coax, 50 Ohm

Part No. PE3W00305				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.17" dia.		650 W	21
12"	24"	36"	48"	60"	50CM	Custom Len.	
$101.36	$106.73	$113.50	$120.26	$127.04	$105.77	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34432				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	22
12"	24"	36"	48"	60"	72"	Custom Len.	
$119.30	$122.42	$125.56	$128.68	$131.81	$143.72	See Web	

RG393/U Coax, 50 Ohm

Part No. PE3338				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	23
12"	24"	36"	48"	60"	72"	Custom Len.	
$119.24	$144.18	$161.97	$180.80	$186.33	$203.10	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34424				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	24
12"	24"	36"	48"	60"	72"	Custom Len.	
$107.36	$114.91	$122.46	$138.31	$137.57	$145.12	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE39229				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	25
12"	24"	36"	48"	60"	-	Custom Len.	
$79.13	$84.39	$94.13	$103.86	$112.00	-	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3895				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	26
12"	24"	36"	48"	60"	72"	Custom Len.	
$100.69	$101.84	$102.98	$104.18	$105.35	$106.51	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE3857				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	27
12"	24"	36"	48"	60"	72"	Custom Len.	
$105.21	$106.91	$107.09	$108.86	$107.21	$112.27	See Web	

SHV PLUG TO SHV JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE3W03078				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.		600 W	28
12"	24"	36"	48"	60"	50CM	Custom Len.	
$100.65	$101.42	$107.90	$112.81	$119.20	$99.08	See Web	

SHV JACK BULKHEAD TO SHV PLUG

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE33018				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	29
12"	24"	36"	48"	60"	-	Custom Len.	
$115.04	$116.16	$117.29	$118.48	$119.63	-	See Web	

SMA MALE TO 1.85MM MALE

Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE36541				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	30
6"	12"	18"	24"	36"	48"	Custom Len.	
$210.81	$210.81	$229.62	$222.41	$234.01	$245.58	See Web	

Standard Flexible Cable Assemblies

PE-P103 Coax, 50 Ohm

Part No. PE3C6633				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.103" dia.	29.48 dB/100ft		31
12"	24"	36"	48"	60"	50CM	Custom Len.	
$250.88	$278.16	$305.47	$332.75	$360.05	$268.34	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE36539				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	32
6"	12"	18"	24"	36"	48"	Custom Len.	
$215.01	$206.53	$210.28	$214.00	$221.44	$228.87	See Web	

SMA MALE TO 2.4MM MALE

Standard Flexible Cable Assemblies

PE-P103 Coax, 50 Ohm

Part No. PE3C6634				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.103" dia.	29.48 dB/100ft		33
12"	24"	36"	48"	60"	50CM	Custom Len.	
$229.12	$256.41	$283.71	$311.01	$338.29	$246.60	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

SMA MALE TO 2.92MM MALE

Standard Flexible Cable Assemblies

PE-P103 Coax, 50 Ohm

Part No. PE3C6632				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.103" dia.	29.48 dB/100ft		34
12"	24"	36"	48"	60"	50CM	Custom Len.	
$222.82	$250.13	$277.42	$304.71	$332.01	$240.30	See Web	

SMA MALE TO 7/16 DIN MALE

Low PIM Formable Cable Assemblies

PE-SR402FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2007				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.			35
100CM	200CM	-	-	-	-	Custom Len.	
$117.74	$127.27	-	-	-	-	See Web	

Standard Formable Cable Assemblies

PE-SR401FL Coax, 50 Ohm

Part No. PE36169				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	36
12"	24"	36"	48"	60"	72"	Custom Len.	
$241.06	$257.26	$273.45	$289.65	$305.86	$322.05	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE36173				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	37
12"	24"	36"	48"	60"	72"	Custom Len.	
$190.55	$198.49	$206.35	$214.30	$222.16	$230.12	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE36157				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	38
12"	24"	36"	48"	60"	72"	Custom Len.	
$231.02	$234.02	$236.95	$239.95	$242.93	$245.87	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3221				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	39
12"	24"	36"	48"	60"	72"	Custom Len.	
$143.77	$144.55	$145.39	$146.19	$146.95	$147.74	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3224				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		40
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.69	$83.78	$89.85	$95.98	$102.05	$106.68	See Web	

RG213/U Coax, 50 Ohm

Part No. PE36159				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	41
12"	24"	36"	48"	60"	72"	Custom Len.	
$229.85	$231.66	$233.48	$235.32	$237.14	$238.88	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3233				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	42
12"	24"	36"	48"	60"	72"	Custom Len.	
$232.72	$240.72	$248.71	$256.72	$264.73	$272.73	See Web	

RG223/U Coax, 50 Ohm

Part No. PE36161				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	43
12"	24"	36"	48"	60"	72"	Custom Len.	
$74.78	$82.69	$81.19	$84.43	$87.60	$90.82	See Web	

RG393/U Coax, 50 Ohm

Part No. PE36163				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W	44
12"	24"	36"	48"	60"	72"	Custom Len.	
$241.63	$258.56	$275.39	$292.32	$309.24	$326.16	See Web	

RG400/U Coax, 50 Ohm

Part No. PE36165				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	45
12"	24"	36"	48"	60"	72"	Custom Len.	
$182.92	$190.55	$198.16	$205.78	$213.40	$220.99	See Web	

Standard Semi-Rigid Cable Assemblies

RG401/U Coax, 50 Ohm

Part No. PE36167				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	46
12"	24"	36"	48"	60"	72"	Custom Len.	
$247.94	$271.03	$294.14	$317.25	$340.27	Call	See Web	

RG402/U Coax, 50 Ohm

Part No. PE36171				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	47
12"	24"	36"	48"	60"	72"	Custom Len.	
$190.29	$197.98	$205.64	$213.34	$220.99	$228.68	See Web	

SMA MALE TO BNC MALE

Flexible Cable Assemblies

LMR-240 Coax, 50 Ohm

Part No. PE3C1830				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		48
12"	24"	36"	48"	60"	50CM	Custom Len.	
$44.39	$43.72	$44.77	$45.83	$46.89	$43.35	See Web	

Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3C0051				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		49
12"	24"	36"	48"	60"	-	Custom Len.	
$36.76	$37.58	$38.42	$39.30	$40.15	-	See Web	

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE34008				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	50
12"	24"	36"	48"	60"	-	Custom Len.	
$76.24	$85.14	$87.17	$95.47	$110.91	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE35109				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	51
12"	24"	36"	48"	60"	-	Custom Len.	
$77.04	$89.79	$102.53	$113.68	$126.25	-	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3615				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	52
12"	24"	36"	48"	60"	72"	Custom Len.	
$44.30	$45.21	$46.10	$47.06	$47.98	$48.90	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3696				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	53
12"	24"	36"	48"	60"	72"	Custom Len.	
$43.55	$53.79	$59.98	$67.04	$73.86	$80.67	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3328				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	54
12"	24"	36"	48"	60"	72"	Custom Len.	
$44.88	$45.52	$46.17	$46.83	$47.51	$48.16	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE33258				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	55
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.85	$74.02	$75.18	$76.41	$72.95	$78.78	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3C2035				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	56
12"	24"	36"	48"	60"	72"	Custom Len.	
$45.96	$48.74	$51.50	$54.43	$53.21	$59.51	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE33523				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	57
12"	24"	36"	48"	60"	72"	Custom Len.	
$76.08	$77.64	$73.47	$74.97	$76.47	$77.98	See Web	

RG213/U Coax, 50 Ohm

Part No. PE36661				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	58
12"	24"	36"	48"	60"	-	Custom Len.	
$126.07	$127.69	$129.32	$130.88	$132.51	-	See Web	

RG214/U Coax, 50 Ohm

Part No. PE33519				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	59
12"	24"	36"	48"	60"	72"	Custom Len.	
$137.01	$144.99	$153.02	$161.00	$169.01	$177.02	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3562				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	60
12"	24"	36"	48"	60"	72"	Custom Len.	
$42.21	$45.43	$48.65	$51.87	$54.57	$57.75	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C2360				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	61
12"	24"	36"	48"	60"	72"	Custom Len.	
$41.69	$45.15	$48.61	$52.28	$55.31	$58.82	See Web	

RG393/U Coax, 50 Ohm

Part No. PE33521				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	62
12"	24"	36"	48"	60"	72"	Custom Len.	
$145.92	$162.78	$179.68	$196.60	$213.52	$230.44	See Web	

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

See Our Website For Current Pricing & Real-Time Stock Availability!

RG400/U Coax, 50 Ohm

Part No. PE3613				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	63
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.17	$63.30	$71.44	$80.04	$88.34	$90.36	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE33989				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	64
12"	24"	36"	48"	60"	-	Custom Len.	
$53.89	$63.93	$74.45	$85.61	$96.34	-	See Web	

RG55B/U Coax, 53 Ohm

Part No. PE3479				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	65
12"	24"	36"	48"	60"	72"	Custom Len.	
$40.27	$45.56	$48.43	$51.47	$54.41	$56.80	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3539				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	66
12"	24"	36"	48"	60"	72"	Custom Len.	
$57.35	$55.16	$56.23	$57.28	$58.32	$63.17	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE3C3321				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	29.15 dB/100ft	240 W	67
12"	24"	36"	48"	60"	72"	Custom Len.	
$47.04	$46.17	$48.80	$51.42	$54.04	$56.15	See Web	

SMA MALE TO BNC MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3C0040				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		68
12"	24"	36"	48"	60"	-	Custom Len.	
$51.98	$52.80	$53.63	$54.02	$54.85	-	See Web	

SMA MALE TO FAKRA PLUG

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE39342A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		69
12"	24"	36"	48"	60"	-	Custom Len.	
$34.53	$39.44	$36.12	$36.86	$37.65	-	See Web	
Part No. PE39342B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		70
12"	24"	36"	48"	60"	-	Custom Len.	
$34.53	$35.33	$36.12	$36.86	$37.65	-	See Web	
Part No. PE39342C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		71
12"	24"	36"	48"	60"	-	Custom Len.	
$37.98	$39.32	$40.66	$42.00	$43.34	-	See Web	
Part No. PE39342D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		72
12"	24"	36"	48"	60"	-	Custom Len.	
$35.71	$37.93	$40.19	$42.40	$44.66	-	See Web	
Part No. PE39342H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		73
12"	24"	36"	48"	60"	-	Custom Len.	
$34.53	$35.33	$36.12	$36.86	$37.65	-	See Web	
Part No. PE39342I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		74
12"	24"	36"	48"	60"	-	Custom Len.	
$35.71	$37.93	$40.19	$42.40	$44.66	-	See Web	
Part No. PE39342K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		75
12"	24"	36"	48"	60"	-	Custom Len.	
$34.53	$35.33	$36.12	$36.86	$37.65	-	See Web	
Part No. PE39342Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		76
12"	24"	36"	48"	60"	-	Custom Len.	
$41.03	$39.32	$40.66	$42.00	$47.03	-	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE39197A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	77
12"	24"	36"	48"	60"	-	Custom Len.	
$48.62	$44.69	$45.17	$45.65	$46.14	-	See Web	
Part No. PE39197C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	78
12"	24"	36"	48"	60"	-	Custom Len.	
$47.75	$44.69	$45.17	$45.65	$46.14	-	See Web	
Part No. PE39197D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	79
12"	24"	36"	48"	60"	-	Custom Len.	
$47.75	$44.69	$45.17	$45.65	$46.14	-	See Web	
Part No. PE39197H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	80
12"	24"	36"	48"	60"	-	Custom Len.	
$40.19	$40.80	$41.39	$41.92	$42.51	-	See Web	
Part No. PE39197I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	81
12"	24"	36"	48"	60"	-	Custom Len.	
$40.19	$40.80	$41.39	$41.92	$42.51	-	See Web	
Part No. PE39197K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	82
12"	24"	36"	48"	60"	-	Custom Len.	
$44.22	$44.69	$45.17	$45.65	$46.14	-	See Web	
Part No. PE39197Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	83
12"	24"	36"	48"	60"	-	Custom Len.	
$48.62	$49.27	$45.17	$45.65	$46.14	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE39343A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	84
12"	24"	36"	48"	60"	-	Custom Len.	
$47.14	$50.34	$53.56	$56.24	$59.42	-	See Web	
Part No. PE39343C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	85
12"	24"	36"	48"	60"	-	Custom Len.	
$51.86	$50.34	$53.56	$56.24	$59.42	-	See Web	
Part No. PE39343D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	86
12"	24"	36"	48"	60"	-	Custom Len.	
$51.32	$49.85	$53.06	$55.74	$58.91	-	See Web	
Part No. PE39343H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	87
12"	24"	36"	48"	60"	-	Custom Len.	
$42.85	$45.97	$49.17	$52.38	$55.06	-	See Web	
Part No. PE39343I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	88
12"	24"	36"	48"	60"	-	Custom Len.	
$42.85	$45.97	$49.17	$52.38	$55.06	-	See Web	
Part No. PE39343K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	89
12"	24"	36"	48"	60"	-	Custom Len.	
$42.85	$45.97	$49.17	$52.38	$55.06	-	See Web	
Part No. PE39343Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	90
12"	24"	36"	48"	60"	-	Custom Len.	
$51.86	$50.34	$53.56	$56.24	$59.42	-	See Web	

SMA MALE TO FAKRA JACK

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE39347A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		91
12"	24"	36"	48"	60"	-	Custom Len.	
$39.30	$40.63	$46.17	$43.30	$44.66	-	See Web	
Part No. PE39347B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		92
12"	24"	36"	48"	60"	-	Custom Len.	
$37.98	$39.32	$40.66	$42.00	$43.34	-	See Web	
Part No. PE39347C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		93
12"	24"	36"	48"	60"	-	Custom Len.	
$39.30	$40.63	$46.17	$43.30	$44.66	-	See Web	
Part No. PE39347D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		94
12"	24"	36"	48"	60"	-	Custom Len.	
$35.71	$37.93	$40.19	$42.40	$44.66	-	See Web	
Part No. PE39347H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		95
12"	24"	36"	48"	60"	-	Custom Len.	
$34.53	$35.33	$36.12	$36.86	$37.65	-	See Web	
Part No. PE39347I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		96
12"	24"	36"	48"	60"	-	Custom Len.	
$34.53	$35.33	$36.12	$36.86	$37.65	-	See Web	
Part No. PE39347K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		97
12"	24"	36"	48"	60"	-	Custom Len.	
$35.71	$37.93	$40.19	$42.40	$44.66	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

Part No. PE39347Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		98
12"	24"	36"	48"	60"	-	Custom Len.	
$40.28	$41.74	$43.22	$41.31	$42.65	-	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE39199A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	99
12"	24"	36"	48"	60"	-	Custom Len.	
$47.75	$44.69	$45.17	$45.65	$46.14	-	See Web	

Part No. PE39199B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	1
12"	24"	36"	48"	60"	-	Custom Len.	
$44.22	$44.69	$45.17	$45.65	$46.14	-	See Web	

Part No. PE39199C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	2
12"	24"	36"	48"	60"	-	Custom Len.	
$48.62	$44.69	$45.17	$50.60	$46.14	-	See Web	

Part No. PE39199D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	3
12"	24"	36"	48"	60"	-	Custom Len.	
$44.22	$48.39	$45.17	$49.71	$46.14	-	See Web	

Part No. PE39199H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	4
12"	24"	36"	48"	60"	-	Custom Len.	
$44.22	$49.27	$45.17	$45.65	$46.14	-	See Web	

Part No. PE39199I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	5
12"	24"	36"	48"	60"	-	Custom Len.	
$40.19	$40.80	$41.39	$41.92	$42.51	-	See Web	

Part No. PE39199K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	6
12"	24"	36"	48"	60"	-	Custom Len.	
$44.22	$44.69	$45.17	$45.65	$46.14	-	See Web	

Part No. PE39199Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	7
12"	24"	36"	48"	60"	-	Custom Len.	
$47.75	$48.39	$49.03	$49.71	$50.36	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE39348A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	8
12"	24"	36"	48"	60"	-	Custom Len.	
$47.14	$50.34	$53.56	$56.24	$59.42	-	See Web	

Part No. PE39348B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	9
12"	24"	36"	48"	60"	-	Custom Len.	
$47.14	$50.34	$53.56	$56.24	$59.42	-	See Web	

Part No. PE39348C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	10
12"	24"	36"	48"	60"	-	Custom Len.	
$50.91	$54.39	$53.56	$56.24	$64.45	-	See Web	

Part No. PE39348D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	11
12"	24"	36"	48"	60"	-	Custom Len.	
$42.85	$45.97	$49.17	$52.38	$55.06	-	See Web	

Part No. PE39348H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	12
12"	24"	36"	48"	60"	-	Custom Len.	
$47.14	$50.34	$53.56	$56.24	$65.39	-	See Web	

Part No. PE39348I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	13
12"	24"	36"	48"	60"	-	Custom Len.	
$42.85	$45.97	$49.17	$52.38	$55.06	-	See Web	

Part No. PE39348K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	14
12"	24"	36"	48"	60"	-	Custom Len.	
$47.14	$54.81	$58.25	$56.24	$59.42	-	See Web	

Part No. PE39348Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	15
12"	24"	36"	48"	60"	-	Custom Len.	
$50.91	$50.34	$53.56	$60.95	$64.45	-	See Web	

SMA MALE TO MC-CARD PLUG

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36112				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	16
12"	24"	36"	48"	60"	72"	Custom Len.	
$45.12	$45.64	$46.13	$46.59	$47.11	$47.58	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36110				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	17
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.12	$54.66	$55.72	$56.77	$57.84	$58.90	See Web	

RG316/U Coax, 50 Ohm

Part No. PE36108				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	18
12"	24"	36"	48"	60"	72"	Custom Len.	
$52.76	$51.32	$54.13	$57.45	$60.73	$64.03	See Web	

SMA MALE TO MCX PLUG

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W07452				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	19
12"	24"	36"	48"	60"	50CM	Custom Len.	
$50.28	$50.90	$51.52	$52.14	$52.76	$50.67	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE33876				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	26.1 dB/100ft	160 W	20
12"	41CM	48CM	56CM	135CM	145CM	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

SMA MALE TO MINI UHF MALE

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3273				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	21
12"	24"	36"	48"	60"	72"	Custom Len.	
$42.89	$43.70	$44.53	$45.34	$46.16	$46.98	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3275				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		22
12"	24"	36"	48"	60"	72"	Custom Len.	
$42.83	$49.19	$55.05	$61.35	$67.65	$73.95	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3271				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	23
12"	24"	36"	48"	60"	72"	Custom Len.	
$44.44	$43.63	$46.83	$50.06	$53.27	$55.97	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3278				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	24
12"	24"	36"	48"	60"	72"	Custom Len.	
$47.91	$55.20	$62.90	$70.64	$78.37	$86.08	See Web	

SMA MALE TO MMCX PLUG

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE34069				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	25
12"	24"	36"	48"	60"	72"	Custom Len.	
$58.22	$58.85	$59.49	$60.16	$55.82	$56.29	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE34374				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	26
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.01	$68.17	$64.17	$65.22	$66.26	$72.95	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34887				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	27
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.53	$64.28	$67.02	$69.92	$65.68	$68.13	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34122				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	28
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.45	$63.90	$67.34	$70.97	$68.68	$77.97	See Web	

SMA MALE TO MMCX PLUG RIGHT ANGLE

Standard Formable Cable Assemblies

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39564				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	29
6"	9"	12"	18"	24"	-	Custom Len.	
$46.10	$43.80	$46.10	Call	$55.55	-	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE34777				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	30
12"	24"	36"	48"	60"	-	Custom Len.	
$72.71	$73.87	$75.03	$76.26	$77.45	-	See Web	

SMA MALE TO N MALE

Flexible Cable Assemblies

LMR-240 Coax, 50 Ohm

Part No. PE3C0102				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		31
12"	24"	36"	48"	60"	-	Custom Len.	
$46.08	$47.17	$48.25	$49.39	$50.49	-	See Web	
Part No. PE3C1982				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		32
12"	24"	36"	48"	60"	50CM	Custom Len.	
$43.91	$43.71	$44.76	$45.82	$46.85	$43.35	See Web	

LMR-195 Coax, 50 Ohm

Part No. PE3C0121				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		33
12"	24"	36"	48"	60"	-	Custom Len.	
$52.00	$52.84	$53.68	$54.04	$54.87	-	See Web	

LMR-240-UF Coax, 50 Ohm

Part No. PE3CA1067				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft		34
12"	24"	36"	48"	60"	72"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38433				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		35
12"	24"	36"	48"	60"	-	Custom Len.	
$46.92	$49.11	$51.38	$55.58	$55.33	-	See Web	

PE-C195 Coax, 50 Ohm

Part No. PE35981				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	36
12"	24"	36"	48"	60"	-	Custom Len.	
$45.95	$46.81	$47.69	$48.60	$49.49	-	See Web	

PE-C200 Coax, 50 Ohm

Part No. PE36200				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10.8 dB/100ft	170 W	37
12"	24"	36"	48"	60"	-	Custom Len.	
$46.62	$50.34	$51.27	$57.50	$62.12	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE38645				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	38
12"	24"	36"	48"	60"	-	Custom Len.	
$58.17	$62.90	$64.16	$65.15	$66.75	-	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3C0044				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		39
12"	24"	36"	48"	60"	-	Custom Len.	
$58.84	$59.92	$60.98	$59.77	$60.85	-	See Web	

LMR-400 Coax, 50 Ohm

Part No. PE3W00832				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.25 dB/100ft		40
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.76	$68.22	$69.69	$71.14	$72.61	$67.69	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE3C0689				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		41
12"	24"	36"	48"	60"	50CM	Custom Len.	
$139.06	$156.68	$174.27	$191.88	$209.48	$150.34	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0132				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			42
12"	18"	24"	36"	48"	60"	Custom Len.	
$389.15	$398.34	$407.53	$425.92	$444.29	$462.68	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0186				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			43
8"	12"	18"	24"	30"	36"	Custom Len.	
$369.32	$374.62	$382.61	$390.56	$398.54	$406.49	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0229				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			44
12"	18"	24"	36"	48"	60"	Custom Len.	
$439.55	$454.90	$470.23	$500.92	$531.60	$562.29	See Web	

LMR-240-UF Coax, 50 Ohm

Part No. PE3W01626				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.							45
12"	24"	36"	48"	60"	50CM	Custom Len.	
$49.84	$51.31	$52.76	$54.22	$55.18	$50.78	See Web	

Precision Formable Cable Assemblies

PE-80TEST Coax, 50 Ohm

Part No. PE3TC0105				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			46
24"	48"	72"	-	-	-	Custom Len.	
$357.55	$450.50	$543.47	-	-	-	See Web	

PE-90TEST Coax, 50 Ohm

Part No. PE3TC0303				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.151" dia.			47
24"	48"	72"	-	-	-	Custom Len.	
$292.28	$373.27	$457.78	-	-	-	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34268				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	48
6"	12"	18"	24"	36"	48"	Custom Len.	
$92.54	$96.44	$100.41	$104.28	$110.58	$118.34	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34263				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	49
6"	12"	18"	24"	36"	48"	Custom Len.	
$142.48	$151.08	$150.87	$159.22	$186.50	$192.62	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE3448				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	50
6"	12"	18"	24"	36"	48"	Custom Len.	
$76.11	$80.42	$84.86	$89.31	$92.45	$100.73	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3657				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	51
6"	12"	18"	24"	36"	48"	Custom Len.	
$89.87	$90.50	$96.36	$102.24	$112.42	$124.00	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3323				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	52
12"	24"	36"	48"	60"	72"	Custom Len.	
$142.61	$137.60	$149.26	$143.75	$146.82	$149.88	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3568				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	53
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.22	$60.41	$67.09	$74.17	$80.98	$87.80	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3291				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	54
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.98	$55.62	$54.32	$56.92	$57.58	$58.23	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3321				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	55
12"	24"	36"	48"	60"	72"	Custom Len.	
$79.00	$80.16	$81.33	$77.70	$78.74	$84.94	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3911				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	56
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.84	$63.04	$60.72	$63.16	$65.60	$68.04	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3422				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	57
12"	24"	36"	48"	60"	72"	Custom Len.	
$141.35	$149.31	$157.25	$165.20	$173.13	$192.84	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3519				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	58
12"	24"	36"	48"	60"	72"	Custom Len.	
$49.56	$53.00	$55.95	$59.57	$63.06	$66.54	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3957				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	59
12"	24"	36"	48"	60"	72"	Custom Len.	
$47.39	$50.50	$53.74	$56.46	$60.97	$64.48	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

RG393/U Coax, 50 Ohm

Part No. PE3302				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	60
12"	24"	36"	48"	60"	72"	Custom Len.	
$150.81	$167.57	$184.35	$214.25	$232.39	$250.50	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3614				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	61
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.04	$72.17	$80.30	$88.90	$97.20	$105.48	See Web	

PE-P141 Coax, 50 Ohm

Part No. PE304				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			62
12"	24"	36"	48"	60"	72"	Custom Len.	
$167.94	$185.30	$197.62	$214.95	$223.19	$235.74	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE3318				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	63
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.81	$74.81	$85.34	$96.48	$107.22	$108.93	See Web	

PE-P142FLX Coax, 50 Ohm

Part No. PE3C0252				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.6 dB/100ft		64
12"	24"	36"	48"	60"	300"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

LMR-240-DB Coax, 50 Ohm

Part No. PE3C3354				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	7.66 dB/100ft		65
12"	50CM	24"	36"	100CM	48"	Custom Len.	
$45.17	$43.41	$43.86	$45.09	$45.44	$46.33	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE34257				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	66
6"	12"	18"	24"	36"	48"	Custom Len.	
$94.05	$99.53	$105.02	$108.89	$128.03	$130.44	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE34261				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	67
6"	12"	18"	24"	36"	48"	Custom Len.	
$93.46	$98.26	$103.10	$107.98	$115.96	$125.56	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34265				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	68
6"	12"	18"	24"	36"	48"	Custom Len.	
$76.56	$81.15	$86.75	$86.91	$97.26	$107.59	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34270				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	69
6"	12"	18"	24"	36"	48"	Custom Len.	
$88.19	$88.19	$92.93	$97.67	$107.18	$115.05	See Web	

RG401/U Coax, 50 Ohm

Part No. PE33001				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	1,400 W	70
6"	12"	18"	24"	36"	48"	Custom Len.	
$146.83	$149.78	$161.67	$173.58	$197.36	$221.16	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3828				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	71
6"	12"	18"	24"	36"	48"	Custom Len.	
$87.33	$91.31	$89.93	$93.71	$107.64	$107.29	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34259				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	72
6"	12"	18"	24"	36"	48"	Custom Len.	
$127.76	$145.57	$158.36	$171.17	$175.45	$194.53	See Web	

Standard Flexible Cable Assemblies

RG55B/U Coax, 53 Ohm

Part No. PE3654				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	73
12"	24"	36"	48"	60"	72"	Custom Len.	
$49.09	$51.57	$57.24	$56.02	$58.50	$60.96	See Web	

SMA MALE TO N MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C1037				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		74
12"	24"	36"	48"	60"	50CM	Custom Len.	
$243.96	$261.57	$279.15	$296.76	$314.36	$255.24	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0134				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			75
12"	18"	24"	36"	48"	60"	Custom Len.	
$513.86	$523.05	$532.24	$550.62	$569.00	$587.40	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0188				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			76
8"	12"	18"	24"	30"	36"	Custom Len.	
$475.62	$480.94	$488.90	$496.87	$504.85	$512.81	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0231				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			77
12"	18"	24"	36"	48"	60"	Custom Len.	
$596.69	$612.04	$627.38	$658.06	$688.75	$719.43	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3236				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		78
12"	24"	36"	48"	60"	50CM	Custom Len.	
$252.78	$280.10	$307.39	$334.69	$361.99	$270.29	See Web	

Part No. PE3C3251				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		79
12"	24"	36"	48"	60"	50CM	Custom Len.	
$400.69	$428.02	$455.34	$482.67	$509.99	$418.20	See Web	

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE3W00507				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	80
12"	24"	36"	48"	60"	50CM	Custom Len.	
$67.01	$75.63	$84.26	$92.88	$101.51	$72.54	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3W00504				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.		450 W	81
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.15	$75.02	$83.90	$92.78	$101.65	$71.84	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3076				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	82
12"	24"	36"	48"	60"	-	Custom Len.	
$68.49	$69.38	$70.28	$71.22	$72.14	-	See Web	

SMA MALE TO N FEMALE

Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3W00177				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		83
12"	24"	36"	48"	60"	50CM	Custom Len.	
$38.66	$54.26	$54.98	$55.69	$56.40	$54.50	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3237				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		84
12"	24"	36"	48"	60"	50CM	Custom Len.	
$236.22	$263.51	$290.81	$318.12	$345.42	$253.71	See Web	

Part No. PE3C3252				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		85
12"	24"	36"	48"	60"	50CM	Custom Len.	
$256.21	$283.54	$310.87	$338.20	$365.50	$273.72	See Web	

Standard Flexible Cable Assemblies

PE-P195 Coax, 50 Ohm

Part No. PE3W00250				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	86
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.17	$76.39	$86.61	$96.84	$107.05	$62.49	See Web	

SMA MALE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C2162				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		87
12"	24"	36"	48"	60"	50CM	Custom Len.	
$194.86	$212.46	$230.04	$247.66	$265.26	$206.14	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0133				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			88
12"	18"	24"	36"	100CM	48"	Custom Len.	
$483.70	$492.88	$502.07	$520.46	$525.61	$538.84	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0187				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			89
8"	12"	18"	24"	30"	36"	Custom Len.	
$479.88	$485.20	$493.16	$501.13	$509.12	$517.07	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0230				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			90
12"	18"	24"	36"	48"	60"	Custom Len.	
$521.60	$536.95	$552.28	$582.96	$613.66	$644.34	See Web	

Precision Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39455				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	91
3"	6"	9"	12"	18"	24"	Custom Len.	
Call	$72.09	$65.54	$72.09	$76.68	$81.27	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39469				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	92
6"	9"	12"	18"	24"	-	Custom Len.	
$59.16	Call	$59.16	$64.09	$69.04	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE39447				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	93
6"	9"	12"	18"	24"	-	Custom Len.	
$29.48	$51.13	$29.48	Call	Call	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39461				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	94
6"	9"	12"	18"	24"	-	Custom Len.	
$56.56	$56.56	Call	$61.17	$65.74	-	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3246				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		95
12"	24"	36"	48"	60"	50CM	Custom Len.	
$318.86	$346.18	$373.51	$400.84	$428.15	$336.36	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34153				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	96
6"	12"	18"	24"	36"	48"	Custom Len.	
$102.56	$106.46	$108.89	$112.74	$120.47	$128.21	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34163				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	97
6"	12"	18"	24"	36"	48"	Custom Len.	
$123.97	$123.97	$132.32	$140.68	$157.38	$174.07	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE33996				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	98
6"	12"	18"	24"	36"	48"	Custom Len.	
$88.13	$88.13	$92.72	$97.31	$106.50	$114.08	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE33844				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	99
6"	12"	18"	24"	36"	48"	Custom Len.	
$89.40	$90.04	$95.93	$101.82	$111.98	$123.59	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3013				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	1
6"	12"	18"	24"	36"	48"	Custom Len.	
$63.28	$65.82	$63.68	$66.72	$67.60	$68.55	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3345				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	2
6"	12"	18"	24"	36"	48"	Custom Len.	
$56.63	$56.49	$63.22	$66.55	$73.24	$80.31	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE34171				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	3
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.46	$71.77	$66.71	$66.94	$67.41	$67.89	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE34174				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	4
6"	12"	18"	24"	36"	48"	Custom Len.	
$70.18	$70.69	$71.23	$71.77	$72.82	$73.86	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE34176				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	5
6"	12"	18"	24"	36"	48"	Custom Len.	
$62.27	$63.45	$64.56	$65.74	$68.13	$70.44	See Web	

RG213/U Coax, 50 Ohm

Part No. PE34185				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	6
6"	12"	18"	24"	36"	48"	Custom Len.	
$138.83	$139.72	$140.57	$141.49	$143.31	$145.13	See Web	

RG214/U Coax, 50 Ohm

Part No. PE33481				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	7
6"	12"	18"	24"	36"	48"	Custom Len.	
$137.22	$137.22	$149.67	$145.19	$153.12	$161.06	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3193				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	8
6"	12"	18"	24"	36"	48"	Custom Len.	
$57.09	$58.77	$56.00	$57.61	$60.80	$63.96	See Web	

RG316/U Coax, 50 Ohm

Part No. PE33555				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	9
5"	6"	12"	18"	24"	36"	Custom Len.	
$73.69	$72.02	$73.69	$69.82	$71.40	$80.55	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE33929				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	10
6"	12"	18"	24"	36"	48"	Custom Len.	
$65.83	$71.10	$67.43	$74.54	$77.96	$75.44	See Web	

RG393/U Coax, 50 Ohm

Part No. PE34183				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W	11
6"	12"	18"	24"	36"	48"	Custom Len.	
$129.91	$138.38	$146.76	$155.22	$172.13	$189.06	See Web	

RG400/U Coax, 50 Ohm

Part No. PE33117				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	12
6"	12"	18"	24"	36"	48"	Custom Len.	
$65.14	$69.06	$68.97	$77.18	$85.31	$93.92	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE34178				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	13
6"	12"	18"	24"	36"	48"	Custom Len.	
$69.43	$74.54	$73.87	$78.74	$88.48	$98.21	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE34148				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	40 dB/100ft	32 W	14
6"	12"	18"	24"	36"	48"	Custom Len.	
$104.08	$108.05	$113.45	$118.77	$129.59	$140.32	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE34151				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	15
6"	12"	18"	24"	36"	48"	Custom Len.	
$103.50	$106.82	$111.55	$116.38	$125.88	$135.44	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34143				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	16
6"	12"	18"	24"	36"	48"	Custom Len.	
$86.70	$92.12	$97.72	$103.33	$107.61	$124.59	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34155				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	17
6"	12"	18"	24"	36"	48"	Custom Len.	
$86.01	$86.01	$90.77	$95.51	$113.92	$112.92	See Web	

RG401/U Coax, 50 Ohm

Part No. PE34157				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	18
6"	12"	18"	24"	36"	48"	Custom Len.	
$131.21	$131.21	$143.12	$155.02	$178.80	$202.59	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3769				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	19
6"	12"	18"	24"	36"	48"	Custom Len.	
$84.54	$89.60	$88.54	$92.56	$100.59	$107.11	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3367				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	20
6"	12"	18"	24"	36"	48"	Custom Len.	
$75.58	$79.28	$82.91	$86.53	$93.86	$101.18	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34159				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	21
6"	12"	18"	24"	36"	48"	Custom Len.	
$110.26	$119.83	$129.32	$138.89	$157.97	$177.02	See Web	

Standard Flexible Cable Assemblies

RG55B/U Coax, 53 Ohm

Part No. PE34169				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	22
6"	12"	18"	24"	36"	48"	Custom Len.	
$53.99	$53.99	$54.74	$55.96	$58.42	$60.88	See Web	

SMA MALE TO QMA MALE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38116				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	23
12"	24"	36"	48"	60"	72"	Custom Len.	
$49.60	$54.43	$51.17	$51.98	$52.76	$53.56	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE38275				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	24
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.65	$56.04	$56.86	$57.67	$58.48	$59.29	See Web	

RG316/U Coax, 50 Ohm

Part No. PE38273				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	25
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.07	$62.23	$65.42	$73.12	$71.77	$74.95	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE38274				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	26
12"	24"	36"	48"	60"	72"	Custom Len.	
$79.36	$78.08	$81.27	$84.48	$87.68	$90.88	See Web	

SMA MALE TO SMA MALE

Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C0113				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		27
12"	24"	36"	48"	60"	-	Custom Len.	
$48.75	$49.59	$50.43	$51.32	$52.17	-	See Web	

LMR-195 Coax, 50 Ohm

Part No. PE3C0038				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		28
12"	24"	36"	48"	60"	-	Custom Len.	
$40.01	$40.85	$41.68	$42.56	$43.40	-	See Web	
Part No. PE3C3055				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		29
12"	24"	36"	48"	60"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5241				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.	11 dB/100ft	560 W	30
12"	24"	36"	48"	60"	50CM	Custom Len.	
$222.74	$245.21	$267.66	$290.11	$312.56	$237.13	See Web	

Semi-Rigid Cable Assemblies

PE-SR402AL Coax, 50 Ohm

Part No. PE3C1398				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	31
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.13	$64.66	$70.18	$81.21	$92.25	$55.19	See Web	

Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5888				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	32
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.07	$69.20	$75.33	$81.47	$87.60	$67.00	See Web	

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE37908				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		33
12"	24"	36"	48"	60"	-	Custom Len.	
$53.95	$54.90	$56.37	$57.91	$59.40	-	See Web	

PE-C195 Coax, 50 Ohm

Part No. PE35784				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	34
12"	24"	36"	48"	60"	-	Custom Len.	
$43.88	$44.75	$45.61	$46.53	$47.41	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE38628				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	35
12"	24"	36"	48"	60"	-	Custom Len.	
$56.11	$60.72	$60.15	$63.18	$66.27	-	See Web	

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C0057				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		36
12"	24"	36"	48"	60"	-	Custom Len.	
$52.72	$53.56	$54.41	$54.78	$55.65	-	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3C0052				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		37
12"	24"	36"	48"	60"	-	Custom Len.	
$55.58	$56.64	$57.72	$58.85	$59.96	-	See Web	
Part No. PE3C0103				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		38
12"	24"	36"	48"	60"	-	Custom Len.	
$42.40	$43.47	$44.56	$45.71	$46.79	-	See Web	

LMR-400-DB Coax, 50 Ohm

Part No. PE3W01582				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.15 dB/100ft		39
12"	24"	36"	48"	60"	50CM	Custom Len.	
$77.93	$79.50	$81.09	$82.67	$84.26	$78.94	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE3C0230				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.32" dia.	7.2 dB/100ft		40
12"	24"	36"	48"	60"	72"	Custom Len.	
$286.87	$306.78	$352.75	$387.74	$481.38	$493.83	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0125				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			41
12"	18"	24"	36"	48"	60"	Custom Len.	
$377.08	$386.27	$395.46	$413.85	$432.22	$450.62	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0180				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			42
8"	12"	18"	24"	30"	36"	Custom Len.	
$369.32	$374.62	$382.61	$390.56	$398.54	$406.49	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0225				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			43
12"	18"	24"	36"	48"	60"	Custom Len.	
$425.86	$441.19	$456.54	$487.22	$517.90	$548.59	See Web	

LMR-240-DB Coax, 50 Ohm

Part No. PE3W03353				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	7.66 dB/100ft		44
12"	24"	36"	48"	60"	50CM	Custom Len.	
$56.66	$57.89	$59.10	$60.31	$61.53	$57.45	See Web	

Precision Formable Cable Assemblies

PE-80TEST Coax, 50 Ohm

Part No. PE3TC0101				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			45
24"	48"	60"	72"	30CM	-	Custom Len.	
$339.94	$432.90	Call	$525.87	Call	-	See Web	
Part No. PE3TC0201				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			46
24"	48"	72"	120"	-	-	Custom Len.	
$492.52	$585.49	$678.45	Call	-	-	See Web	

PE-90TEST Coax, 50 Ohm

Part No. PE3TC0301				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.151" dia.			47
24"	48"	72"	-	-	-	Custom Len.	
$250.04	$355.66	$440.17	-	-	-	See Web	
Part No. PE3TC0401				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.151" dia.			48
24"	30"	48"	72"	250CM	393.701//	Custom Len.	
$423.75	Call	$508.25	$592.76	Call	Call	See Web	

Precision Flexible Cable Assemblies

PE-P141 Coax, 50 Ohm

Part No. PE312				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			49
30CM	24"	36"	48"	60"	72"	Custom Len.	
Call	$177.58	$176.25	$160.15	$178.95	$177.67	See Web	
Part No. PE3CA1130				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			50
12"	18"	24"	36"	48"	60"	Custom Len.	
$138.43	Call	$144.50	$155.77	$154.06	$178.31	See Web	

Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

Low PIM Formable Cable Assemblies

PE-SR402FLJ Low PIM Coax, 50 Ohm

Part No. PE3C2008				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.			51
12"	30"	40"	60"	70"	75"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7863				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		52
12"	24"	36"	48"	60"	50CM	Custom Len.	
$48.66	$52.43	$55.68	$59.40	$63.13	$51.07	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6207				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	53
12"	24"	36"	48"	60"	50CM	Custom Len.	
$47.54	$53.73	$59.37	$65.51	$71.64	$51.49	See Web	

Test Flexible Cable Assemblies

PE-P160 Coax, 50 Ohm

Part No. PE366				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.	12.62 dB/100ft		54
12"	24"	36"	48"	60"	50CM	Custom Len.	
Call	Call	$353.33	$380.59	Call	Call	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE333				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	4.6 dB/100ft		55
12"	24"	36"	48"	60"	50CM	Custom Len.	
$264.57	$292.69	$320.81	$348.94	$377.07	$282.60	See Web	
Part No. PE336				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			56
12"	24"	36"	48"	60"	72"	Custom Len.	
$255.60	$283.73	$311.85	$345.81	$368.09	$408.73	See Web	
Part No. PE3C3235				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		57
12"	24"	36"	48"	60"	50CM	Custom Len.	
$166.70	$194.02	$221.30	$248.61	$275.91	$184.21	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE341				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		58
12"	24"	36"	48"	60"	46CM	Custom Len.	
$121.36	$138.97	$156.56	$174.18	$191.78	Call	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34186				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	59
6"	12"	18"	24"	36"	48"	Custom Len.	
$97.00	$101.33	$105.80	$103.70	$110.26	$118.25	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34188				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					6.8 dB/100ft	279 W	60
6"	12"	18"	24"	36"	48"	Custom Len.	
$131.51	$140.11	$148.97	$157.81	$192.43	$209.14	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE3481				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	400 W	61
6"	12"	18"	24"	36"	48"	Custom Len.	
$48.32	$52.68	$56.64	$61.07	$69.97	$79.36	See Web	
Part No. PE39423				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	400 W	62
3"	6"	9"	12"	18"	24"	Custom Len.	
$51.57	$50.60	$48.42	$50.60	$56.51	$62.88	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39437				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	63
6"	9"	12"	18"	24"	-	Custom Len.	
$63.50	$61.28	$63.50	$68.44	$73.37	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3867				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	64
6"	12"	18"	24"	36"	48"	Custom Len.	
$55.53	$61.58	$67.83	$74.06	$81.61	$93.37	See Web	
Part No. PE39415				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	65
6"	9"	12"	18"	24"	-	Custom Len.	
$55.02	$53.44	$55.02	$61.15	$67.29	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39429				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	66
6"	9"	12"	18"	24"	-	Custom Len.	
$54.97	$54.97	$54.97	$59.90	$64.84	-	See Web	

Standard Flexible Cable Assemblies

RG8X Coax, 50 Ohm

Part No. PE39087				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13.5 dB/100ft	60 W	67
12"	24"	36"	48"	60"	-	Custom Len.	
$70.06	$73.43	$82.04	$86.15	$90.11	-	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3369				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	68
6"	12"	18"	24"	36"	48"	Custom Len.	
$47.75	$50.62	$48.17	$48.56	$49.39	$50.21	See Web	
Part No. PE36689				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	69
24"	36"	48"	-	-	-	Custom Len.	
$122.16	$115.96	$123.97	-	-	-	See Web	
Part No. PE36690				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	80 W	70
24"	36"	48"	72"	-	-	Custom Len.	
$146.02	$146.94	$147.88	$149.74	-	-	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3385				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	600 W	71
6"	12"	18"	24"	36"	48"	Custom Len.	
$54.63	$57.88	$61.22	$64.56	$71.24	$78.32	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3353				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	72
6"	12"	18"	24"	36"	48"	Custom Len.	
$54.06	$54.37	$54.19	$54.51	$55.14	$55.82	See Web	
Part No. PE3W00365				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft		73
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.16	$69.77	$70.39	$71.00	$67.69	$65.61	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3574				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	74
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.99	$72.55	$73.13	$73.71	$74.88	$76.11	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3361				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	75
6"	12"	18"	24"	36"	48"	Custom Len.	
$54.32	$55.66	$57.03	$58.39	$61.14	$64.04	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE3778				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	76
12"	24"	36"	48"	60"	-	Custom Len.	
$59.80	$60.16	$67.56	$67.65	$75.59	-	See Web	

RG213/U Coax, 50 Ohm

Part No. PE35571				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	77
12"	24"	36"	48"	60"	-	Custom Len.	
$184.37	$186.00	$187.56	$189.18	$190.82	-	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3121				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	78
6"	12"	18"	24"	36"	48"	Custom Len.	
$214.27	$214.27	$218.24	$222.21	$230.16	$238.10	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3377				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	79
6"	12"	18"	24"	36"	48"	Custom Len.	
$42.77	$42.77	$44.37	$45.97	$49.19	$52.40	See Web	
Part No. PE3W02458				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	80
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.25	$80.72	$84.28	$87.84	$91.41	$79.43	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3573				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	81
6"	12"	18"	24"	36"	48"	Custom Len.	
$54.43	$55.60	$57.32	$59.04	$62.47	$66.11	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3704				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	82
12"	48CM	53CM	24"	36"	104CM	Custom Len.	
$54.35	Call	Call	$57.77	$61.22	Call	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3500				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	83
6"	12"	18"	24"	36"	48"	Custom Len.	
$56.89	$60.83	$64.90	$68.95	$77.10	$85.70	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-P086EAM Coax, 50 Ohm

Part No. PE3CA1039				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.104" dia.			84
7"	8"	9"	12"	14"	16"	Custom Len.	
$62.61	Call	Call	$63.75	Call	Call	See Web	

PE-P141 Coax, 50 Ohm

Part No. PE300				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.	11.2 dB/100ft	600 W	85
12"	24"	36"	48"	60"	72"	Custom Len.	
$124.57	$138.94	$153.32	$167.70	$182.08	$196.45	See Web	
Part No. PE350				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.	11.2 dB/100ft	600 W	86
12"	24"	36"	48"	60"	72"	Custom Len.	
$99.66	$109.53	$125.83	$138.87	$143.33	$163.97	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE3138				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	87
6"	12"	18"	24"	36"	48"	Custom Len.	
$64.58	$64.58	$70.32	$76.05	$87.51	$98.95	See Web	

LMR-195 Coax, 50 Ohm

Part No. PE3C0116				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		88
12"	24"	36"	48"	60"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

PE-P141FLX Coax, 50 Ohm

Part No. PE3CA1035				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			89
13CM	12"	24"	36"	48"	72"	Custom Len.	
Call	$77.56	$98.57	$110.41	Call	Call	See Web	

PE-P103 Coax, 50 Ohm

Part No. PE3C6631				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.103" dia.	29.48 dB/100ft		90
12"	24"	36"	48"	60"	50CM	Custom Len.	
$215.20	$243.30	$266.88	$295.10	$323.32	$228.51	See Web	

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA1801				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			91
24"	48"	96"	240"	400"	-	Custom Len.	
$842.31	$939.16	Call	$1,771.71	Call	-	See Web	

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0023				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			92
12"	18"	24"	30"	36"	48"	Custom Len.	
$237.03	$239.98	$242.94	$245.89	$248.86	$254.76	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0051				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			93
12"	18"	24"	30"	36"	48"	Custom Len.	
$241.70	$246.98	$252.26	$257.55	$262.85	$273.42	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0079				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			94
12"	18"	24"	30"	36"	48"	Custom Len.	
$238.64	$242.40	$246.16	$249.92	$253.69	$261.21	See Web	

M17/113-RG316-27478 Coax, 50 Ohm

Part No. PE3M0090				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.			95
6"	8"	12"	16"	18"	24"	Custom Len.	
$187.75	$188.11	$188.84	$189.55	$189.94	$191.01	See Web	

M17/119-RG174-0XDS2 Coax, 50 Ohm

Part No. PE3M0105				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.			96
6"	8"	12"	16"	18"	24"	Custom Len.	
$187.09	$187.22	$187.51	$187.79	$187.95	$188.35	See Web	

M17/28-RG058-0XDS2 Coax, 50 Ohm

Part No. PE3M0119				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			97
12"	18"	24"	30"	36"	48"	Custom Len.	
$350.33	$350.97	$351.61	$352.26	$352.91	$354.21	See Web	

RG55B/U Coax, 53 Ohm

Part No. PE3572				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	98
6"	12"	18"	24"	36"	48"	Custom Len.	
$46.83	$49.65	$48.08	$52.53	$51.82	$54.31	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3814				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	99
6"	12"	18"	24"	36"	48"	Custom Len.	
$73.95	$78.39	$74.47	$75.01	$76.07	$77.13	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE3739				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	1
6"	12"	18"	24"	36"	48"	Custom Len.	
$51.90	$53.26	$54.19	$55.60	$58.40	$57.60	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE38059				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	2
12"	24"	36"	48"	60"	-	Custom Len.	
$53.77	$60.67	$60.21	$63.64	$67.06	-	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE3899				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	3
6"	12"	18"	24"	36"	48"	Custom Len.	
$74.46	$74.46	$75.23	$75.97	$77.47	$79.00	See Web	

RG180B/U Coax, 95 Ohm

Part No. PE3245				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.		250 W	4
12"	24"	36"	48"	60"	-	Custom Len.	
$69.97	$70.40	$74.78	$84.49	$89.34	-	See Web	

Standard Semi-Rigid Cable Assemblies

PE-020SR Coax, 50 Ohm

Part No. PE34191				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					85 dB/100ft	2.9 W	5
6"	12"	18"	24"	36"	48"	Custom Len.	
$145.76	$155.98	$166.52	$177.04	$186.51	$206.18	See Web	

PE-034SR Coax, 50 Ohm

Part No. PE34193				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					60 dB/100ft	10 W	6
6"	12"	18"	24"	36"	48"	Custom Len.	
$150.27	$147.87	$154.50	$170.07	$183.41	$187.83	See Web	

PE-047SR Coax, 50 Ohm

Part No. PE3656				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	7
6"	12"	18"	24"	36"	48"	Custom Len.	
$96.46	$102.84	$107.88	$114.34	$119.17	$140.98	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE3387				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	8
6"	12"	18"	24"	36"	48"	Custom Len.	
$97.96	$103.39	$102.52	$107.53	$124.01	$125.71	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34180				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	9
6"	12"	18"	24"	36"	48"	Custom Len.	
$56.27	$61.72	$67.30	$72.89	$84.08	$95.92	See Web	

PE-SR402TN Coax, 50 Ohm

Part No. PE3C1015				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft		10
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.97	$62.61	$62.62	$68.49	$74.35	$80.21	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34182				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	11
6"	12"	18"	24"	36"	48"	Custom Len.	
$53.35	$57.94	$63.17	$68.39	$78.86	$84.22	See Web	

RG401/U Coax, 50 Ohm

Part No. PE33003				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	1,400 W	12
6"	12"	18"	24"	36"	48"	Custom Len.	
$145.13	$157.07	$169.36	$171.97	$206.22	$232.23	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3492				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	13
6"	12"	18"	24"	36"	48"	Custom Len.	
$54.49	$58.66	$62.97	$67.27	$75.86	$84.97	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3818				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	14
6"	12"	18"	24"	36"	48"	Custom Len.	
$52.43	$55.92	$60.00	$64.08	$72.26	$80.89	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34184				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	15
6"	12"	18"	24"	36"	48"	Custom Len.	
$143.99	$152.63	$153.83	$163.66	$183.32	$203.00	See Web	

SMA MALE TO SMA MALE RIGHT ANGLE

Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5894				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	16
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.66	$70.80	$109.67	$83.07	$89.21	$68.60	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

For our complete selection of cable assemblies, please visit our website

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE36475				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	17
12"	24"	36"	48"	60"	-	Custom Len.	
$51.46	$52.32	$49.24	$50.03	$50.82	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE38624				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	18
12"	24"	36"	48"	60"	-	Custom Len.	
$73.15	$74.41	$71.28	$74.34	$77.44	-	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3C0104				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		19
12"	24"	36"	48"	60"	-	Custom Len.	
$46.84	$46.11	$47.19	$50.16	$51.25	-	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5246				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			20
12"	24"	36"	48"	60"	50CM	Custom Len.	
$262.97	$285.44	$307.90	$330.36	$352.80	$277.36	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0128				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			21
12"	18"	24"	36"	48"	60"	Custom Len.	
$485.70	$494.88	$504.07	$522.46	$540.83	$559.23	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0182				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			22
8"	12"	18"	24"	30"	36"	Custom Len.	
$484.14	$489.47	$497.43	$505.41	$513.38	$521.34	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0226				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			23
12"	18"	24"	36"	48"	60"	Custom Len.	
$561.21	$576.55	$591.89	$622.57	$653.27	$683.95	See Web	

Precision Flexible Cable Assemblies

PE-P141 Coax, 50 Ohm

Part No. PE351				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			24
6"	12"	24"	36"	48"	60"	Custom Len.	
$178.82	$184.80	$189.31	$209.43	$222.45	$235.01	See Web	
Part No. PE3C0806				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.	11.2 dB/100ft	550 W	25
12"	24"	36"	48"	60"	72"	Custom Len.	
$152.09	$164.33	$176.60	$188.87	$201.12	$213.39	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7864				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		26
12"	24"	36"	48"	60"	50CM	Custom Len.	
$49.77	$53.53	$56.77	$60.51	$64.23	$52.18	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6210				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	27
12"	24"	36"	48"	60"	50CM	Custom Len.	
$52.84	$58.49	$64.62	$70.76	$76.88	$56.27	See Web	

Test Flexible Cable Assemblies

PE-P160 Coax, 50 Ohm

Part No. PE367				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.	12.62 dB/100ft		28
12"	24"	36"	48"	60"	50CM	Custom Len.	
Call	Call	$379.08	$406.33	Call	Call	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C1722				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		29
12"	24"	36"	48"	60"	50CM	Custom Len.	
$282.95	$311.08	$339.19	$367.31	$395.43	$300.96	See Web	
Part No. PE3C3248				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		30
12"	24"	36"	48"	60"	50CM	Custom Len.	
$360.68	$388.01	$415.33	$442.65	$469.98	$378.18	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34197				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	31
6"	12"	18"	24"	36"	48"	Custom Len.	
$130.67	$138.52	$134.66	$138.67	$146.66	$154.64	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34202				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					6.8 dB/100ft	279 W	32
6"	12"	18"	24"	36"	48"	Custom Len.	
$156.82	$157.69	$166.55	$175.40	$190.18	$206.89	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE3483				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	400 W	33
6"	12"	18"	24"	36"	48"	Custom Len.	
$62.26	$66.57	$71.01	$75.45	$84.34	$96.25	See Web	
Part No. PE39425				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	400 W	34
6"	9"	12"	18"	24"	-	Custom Len.	
$47.94	$45.77	$47.94	$52.59	$56.69	-	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39439				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	35
6"	9"	12"	18"	24"	-	Custom Len.	
$56.10	$52.43	$56.10	$60.85	$65.60	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE39417				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	36
6"	9"	12"	18"	24"	-	Custom Len.	
$54.49	$51.55	$54.49	$60.13	$66.26	-	See Web	
Part No. PE3958				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	37
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.44	$81.60	$87.48	$93.36	$105.12	$115.26	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W02993				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	121.5 W	38
12"	24"	36"	48"	60"	50CM	Custom Len.	
$53.53	$62.88	$72.73	$82.58	$92.43	$59.36	See Web	
Part No. PE3W03751				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	121.5 W	39
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.06	$81.91	$91.75	$101.60	$109.89	$78.38	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3319				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	40
6"	12"	18"	24"	36"	48"	Custom Len.	
$61.12	$61.54	$62.00	$62.44	$58.59	$59.42	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3512				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	41
6"	12"	18"	24"	36"	48"	Custom Len.	
$57.83	$61.07	$64.43	$67.75	$74.44	$75.48	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3420				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	42
6"	12"	18"	24"	36"	48"	Custom Len.	
$70.20	$70.52	$70.83	$71.16	$71.79	$67.97	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3865				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	43
6"	12"	18"	24"	36"	48"	Custom Len.	
$88.60	$89.15	$83.09	$83.60	$84.66	$85.72	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3510				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	44
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.39	$72.73	$68.55	$69.78	$78.22	$81.10	See Web	
Part No. PE3W04442				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	45
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.65	$62.59	$65.53	$68.47	$71.39	$61.52	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE3779				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	46
6"	12"	18"	24"	36"	48"	Custom Len.	
$58.83	$60.71	$62.64	$64.57	$63.68	$67.42	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3429				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	47
6"	12"	18"	24"	36"	48"	Custom Len.	
$63.45	$65.11	$66.82	$68.54	$71.97	$75.58	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3513				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	48
6"	12"	18"	24"	36"	48"	Custom Len.	
$70.70	$72.38	$74.09	$72.76	$79.24	$82.87	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

RG316-DS Coax, 50 Ohm

Part No. PE3344				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	49
6"	12"	18"	24"	36"	48"	Custom Len.	
$62.23	$62.23	$63.84	$65.43	$68.64	$71.84	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3003				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	50
6"	12"	18"	24"	36"	48"	Custom Len.	
$70.14	$74.09	$78.15	$82.23	$90.35	$98.95	See Web	

PE-P086EAM Coax, 50 Ohm

Part No. PE3CA1040				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.104" dia.			51
12"	24"	36"	50CM	100CM	102CM	Custom Len.	
$68.78	$82.25	$95.69	$77.31	$90.46	Call	See Web	

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1036				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			52
10"	11"	12"	14.500//	16"	24"	Custom Len.	
$79.54	$79.54	$79.55	Call		$100.53	See Web	

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0024				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			53
12"	18"	24"	30"	36"	48"	Custom Len.	
$303.76	$279.10	$282.24	$285.02	$287.98	$293.88	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0052				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			54
12"	18"	24"	30"	36"	48"	Custom Len.	
$280.81	$286.09	$291.39	$296.67	$301.96	$312.54	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0080				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			55
12"	18"	24"	30"	36"	48"	Custom Len.	
$277.77	$281.52	$285.29	$289.04	$292.82	$300.33	See Web	

M17/113-RG316-27478 Coax, 50 Ohm

Part No. PE3M0091				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.			56
6"	8"	12"	16"	18"	24"	Custom Len.	
$204.96	$205.31	$226.64	$206.76	$207.13	$208.21	See Web	

M17/119-RG174-0XDS2 Coax, 50 Ohm

Part No. PE3M0106				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.			57
6"	8"	12"	16"	18"	24"	Custom Len.	
$204.29	$204.42	$204.71	$204.99	$205.13	$205.56	See Web	

M17/28-RG058-0XDS2 Coax, 50 Ohm

Part No. PE3M0120				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			58
12"	18"	24"	30"	36"	48"	Custom Len.	
$284.55	$285.19	$285.85	$286.49	$287.14	$288.44	See Web	

SMA MALE TO SMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

M17/113-RG316-27478 Coax, 50 Ohm

Part No. PE3M0092				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.			59
6"	8"	12"	16"	18"	24"	Custom Len.	
$194.93	$195.28	$196.02	$196.73	$197.10	$198.19	See Web	

M17/119-RG174-0XDS2 Coax, 50 Ohm

Part No. PE3M0107				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.			60
6"	8"	12"	16"	18"	24"	Custom Len.	
$194.27	$194.40	$194.69	$194.96	$195.10	$195.53	See Web	

SMA MALE TO SMA MALE RIGHT ANGLE

Standard Semi-Rigid Cable Assemblies

PE-020SR Coax, 50 Ohm

Part No. PE34204				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					85 dB/100ft	2.9 W	61
6"	12"	18"	24"	36"	48"	Custom Len.	
$148.52	$173.89	$167.58	$177.15	$196.21	$215.27	See Web	

PE-034SR Coax, 50 Ohm

Part No. PE34206				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					60 dB/100ft	10 W	62
6"	12"	18"	24"	36"	48"	Custom Len.	
$143.11	$149.74	$156.45	$163.10	$176.43	$189.77	See Web	

PE-047SR Coax, 50 Ohm

Part No. PE3230				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	63
6"	12"	18"	24"	36"	48"	Custom Len.	
$133.92	$133.92	$139.46	$145.00	$156.10	$167.21	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE3393				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	64
6"	12"	18"	24"	36"	48"	Custom Len.	
$120.34	$125.09	$129.86	$134.59	$144.15	$153.72	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34195				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	65
6"	12"	18"	24"	36"	48"	Custom Len.	
$72.53	$77.95	$78.72	$83.88	$94.25	$104.58	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34199				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	66
6"	12"	18"	24"	36"	48"	Custom Len.	
$70.18	$74.73	$79.34	$83.97	$93.13	$102.37	See Web	

RG401/U Coax, 50 Ohm

Part No. PE34220				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	67
6"	12"	18"	24"	36"	48"	Custom Len.	
$158.37	$170.31	$166.36	$177.87	$200.97	$224.06	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3821				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	68
6"	12"	18"	24"	36"	48"	Custom Len.	
$74.14	$78.32	$76.52	$80.54	$88.56	$96.61	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3822				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	69
6"	12"	18"	24"	36"	48"	Custom Len.	
$78.72	$78.72	$82.52	$86.29	$101.34	$101.37	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34200				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	70
6"	12"	18"	24"	36"	48"	Custom Len.	
$147.42	$150.80	$160.31	$169.85	$188.93	$208.00	See Web	

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE3137				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	71
6"	12"	18"	24"	36"	48"	Custom Len.	
$75.53	$76.05	$76.50	$77.04	$78.01	$79.03	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE3459				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	72
6"	12"	18"	24"	36"	48"	Custom Len.	
$68.89	$68.89	$70.18	$71.49	$74.09	$76.68	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE3411				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	73
6"	12"	18"	24"	36"	48"	Custom Len.	
$75.79	$76.50	$77.24	$77.96	$79.43	$80.86	See Web	

RG180B/U Coax, 95 Ohm

Part No. PE3352				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.145" dia.		250 W	74
6"	12"	18"	24"	36"	48"	Custom Len.	
$65.23	$67.34	$69.44	$71.55	$75.86	$80.08	See Web	

SMA MALE TO SMA FEMALE

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE37995				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		75
12"	24"	36"	48"	60"	-	Custom Len.	
$58.18	$55.18	$56.51	$57.82	$64.12	-	See Web	

PE-C195 Coax, 50 Ohm

Part No. PE36201				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	76
12"	24"	36"	48"	60"	-	Custom Len.	
$52.14	$53.00	$50.78	$51.56	$52.35	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE38638				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	77
12"	24"	36"	48"	60"	-	Custom Len.	
$60.05	$61.13	$62.85	$65.88	$68.75	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE39148				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	78
12"	24"	36"	48"	60"	-	Custom Len.	
$102.79	$104.24	$105.67	$107.13	$107.07	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

LMR-240 Coax, 50 Ohm

Part No. PE3W02466				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.			79
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.28	$54.80	$55.84	$56.88	$57.91	$54.45	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE340				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft	820 W	80
12"	24"	36"	48"	60"	50CM	Custom Len.	
$164.20	$181.80	$199.42	$217.01	$234.61	$175.49	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0126				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			81
12"	18"	24"	36"	48"	60"	Custom Len.	
$449.49	$458.68	$467.87	$486.25	$504.63	$523.03	See Web	

LMR-240-UF Coax, 50 Ohm

Part No. PE3W04971				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.19 dB/100ft		82
12"	24"	36"	48"	60"	50CM	Custom Len.	
$52.58	$54.06	$55.05	$56.53	$58.01	$53.52	See Web	

Precision Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39426				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	83
6"	9"	12"	18"	24"	-	Custom Len.	
$44.72	$40.64	$44.72	$49.17	$53.63	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE39418				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	84
6"	9"	12"	18"	24"	-	Custom Len.	
$42.09	$44.63	$44.63	$50.57	$55.97	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39432				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	85
6"	9"	12"	18"	24"	-	Custom Len.	
$42.08	$39.69	$42.08	$46.87	$51.66	-	See Web	

PE-80TEST Coax, 50 Ohm

Part No. PE3TC0102				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			86
24"	48"	72"	-	-	-	Custom Len.	
$386.89	$479.84	$572.80	-	-	-	See Web	

Part No. PE3TC0202				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			87
24"	48"	72"	-	-	-	Custom Len.	
$600.12	$693.08	$786.03	-	-	-	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7865				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		88
12"	24"	36"	48"	60"	50CM	Custom Len.	
$49.22	$52.98	$56.23	$59.96	$63.68	$51.63	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5883				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			89
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.87	$70.00	$76.13	$82.27	$88.40	$67.79	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34228				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	90
6"	12"	18"	24"	36"	48"	Custom Len.	
$105.25	$105.25	$118.56	$111.78	$119.77	$127.76	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34233				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	91
6"	12"	18"	24"	36"	48"	Custom Len.	
$125.97	$125.97	$134.31	$142.66	$159.37	$176.05	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE3443				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	92
6"	12"	18"	24"	36"	48"	Custom Len.	
$62.74	$67.06	$66.23	$70.38	$78.67	$86.96	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39440				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	93
6"	9"	12"	18"	24"	-	Custom Len.	
$42.91	Call	$42.91	Call	$52.87	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3651				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	94
6"	12"	18"	24"	36"	48"	Custom Len.	
$76.58	$76.58	$88.94	$95.17	$100.09	$110.30	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3078				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	95
6"	12"	18"	24"	36"	48"	Custom Len.	
$58.38	$63.06	$58.80	$59.19	$64.84	$60.82	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3611				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	96
6"	12"	18"	24"	36"	48"	Custom Len.	
$56.60	$59.84	$57.58	$60.71	$73.21	$73.32	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3715				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	97
6"	12"	18"	24"	36"	48"	Custom Len.	
$61.67	$61.99	$62.30	$58.94	$63.25	$63.92	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3056				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	98
6"	12"	18"	24"	36"	48"	Custom Len.	
$76.21	$72.43	$72.97	$77.94	$79.10	$75.59	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3706				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	99
6"	12"	18"	24"	36"	48"	Custom Len.	
$61.60	$61.60	$62.81	$64.04	$66.48	$68.92	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3697				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	1
6"	12"	18"	24"	36"	48"	Custom Len.	
$52.12	$53.80	$55.02	$56.73	$60.15	$59.85	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3832				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	2
6"	12"	18"	24"	36"	48"	Custom Len.	
$63.57	$65.24	$66.96	$68.67	$67.90	$75.76	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3171				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	3
6"	12"	18"	24"	36"	48"	Custom Len.	
$69.43	$65.83	$67.43	$74.54	$77.96	$75.44	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3864				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	4
6"	12"	18"	24"	36"	48"	Custom Len.	
$63.47	$63.47	$67.31	$71.13	$78.79	$86.46	See Web	

PE-P141 Coax, 50 Ohm

Part No. PE3C1876				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.	11.2 dB/100ft	550 W	5
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.05	$72.02	$85.00	$97.97	$109.41	$67.35	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE3160				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	6
6"	12"	18"	24"	36"	48"	Custom Len.	
$68.80	$72.93	$73.65	$78.53	$88.26	$98.00	See Web	

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA1802				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			7
24"	48"	-	-	-	-	Custom Len.	
$858.46	$954.71	-	-	-	-	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3333				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	8
6"	12"	18"	24"	36"	48"	Custom Len.	
$76.20	$76.20	$76.73	$81.92	$78.32	$79.37	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE3102				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	29.15 dB/100ft		9
6"	12"	18"	24"	36"	48"	Custom Len.	
$61.89	$68.08	$63.18	$64.48	$67.08	$76.68	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE3405				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	10
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.62	$72.35	$73.07	$73.80	$75.26	$76.71	See Web	

Standard Semi-Rigid Cable Assemblies

PE-020SR Coax, 50 Ohm

Part No. PE34224				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					85 dB/100ft	2.9 W	11
6"	12"	18"	24"	36"	48"	Custom Len.	
$147.41	$156.96	$166.48	$176.03	$195.09	$214.16	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-034SR Coax, 50 Ohm

Part No. PE34226				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					60 dB/100ft	10 W	12
6"	12"	18"	24"	36"	48"	Custom Len.	
$158.74	$158.74	$165.40	$172.07	$185.39	$209.04	See Web	

PE-047SR Coax, 50 Ohm

Part No. PE3188				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	13
6"	12"	18"	24"	36"	48"	Custom Len.	
$106.94	$106.94	$112.49	$118.05	$129.15	$140.24	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE3253				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					41 dB/100ft	32 W	14
6"	12"	18"	24"	36"	48"	Custom Len.	
$101.75	$101.11	$105.93	$109.22	$118.77	$128.27	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34235				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	15
6"	12"	18"	24"	36"	48"	Custom Len.	
$62.63	$68.06	$73.65	$75.80	$86.12	$96.48	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34237				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	16
6"	12"	18"	24"	36"	48"	Custom Len.	
$64.10	$68.74	$73.35	$77.89	$87.12	$96.31	See Web	

RG401/U Coax, 50 Ohm

Part No. PE33896				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	17
6"	12"	18"	24"	36"	48"	Custom Len.	
$133.29	$133.29	$153.58	$157.09	$180.88	$204.68	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3823				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	18
6"	12"	18"	24"	36"	48"	Custom Len.	
$62.67	$63.06	$71.14	$71.09	$79.13	$93.14	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3824				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	19
6"	12"	18"	24"	36"	48"	Custom Len.	
$73.96	$72.16	$75.94	$79.72	$87.26	$94.83	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34230				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	20
6"	12"	18"	24"	36"	48"	Custom Len.	
$112.20	$121.72	$131.26	$140.78	$159.84	$178.92	See Web	

Standard Flexible Cable Assemblies

RG55B/U Coax, 53 Ohm

Part No. PE3093				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	21
6"	12"	18"	24"	36"	48"	Custom Len.	
$44.99	$46.19	$47.39	$48.56	$50.97	$53.38	See Web	

SMA MALE TO SMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38240				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		22
12"	24"	36"	48"	60"	-	Custom Len.	
$57.93	$54.94	$56.28	$57.61	$58.92	-	See Web	

PE-C195 Coax, 50 Ohm

Part No. PE36417				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	23
12"	24"	36"	48"	60"	-	Custom Len.	
$44.12	$45.58	$47.05	$48.51	$50.05	-	See Web	

LMR-195 Coax, 50 Ohm

Part No. PE3C5767				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		24
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.15	$54.83	$55.17	$55.85	$56.53	$54.24	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5242				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			25
12"	24"	36"	48"	60"	50CM	Custom Len.	
$241.18	$263.65	$286.09	$308.56	$331.01	$255.57	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0127				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			26
12"	18"	24"	36"	48"	60"	Custom Len.	
$484.90	$494.09	$503.27	$521.66	$540.05	$558.43	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0181				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			27
8"	12"	18"	24"	30"	36"	Custom Len.	
$479.88	$485.20	$493.16	$501.13	$509.12	$517.07	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7866				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		28
12"	24"	36"	48"	60"	50CM	Custom Len.	
$52.00	$55.25	$58.97	$62.70	$66.42	$54.41	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34245				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	29
6"	12"	18"	24"	36"	48"	Custom Len.	
$107.77	$111.63	$115.53	$119.37	$127.11	$134.86	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34249				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	30
6"	12"	18"	24"	36"	48"	Custom Len.	
$120.85	$129.00	$137.07	$145.21	$161.40	$177.59	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39441				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	31
6"	9"	12"	18"	24"	-	Custom Len.	
$45.26	$41.14	$45.26	$50.06	$54.34	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE39419				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	32
4"	6"	9"	12"	18"	24"	Custom Len.	
$48.35	$54.50	$52.05	$54.50	$60.64	$66.77	See Web	

Part No. PE3961				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	33
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.50	$77.55	$83.79	$83.55	$95.33	$107.09	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39433				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	34
6"	9"	12"	18"	24"	-	Custom Len.	
$20.96	$43.80	$20.96	$25.88	$29.98	-	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3956				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			35
6"	12"	18"	24"	36"	48"	Custom Len.	
$52.59	$52.98	$53.38	$53.77	$54.08	$54.93	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3494				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	36
6"	12"	18"	24"	36"	48"	Custom Len.	
$60.21	$63.45	$66.80	$70.13	$71.36	$83.90	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3184				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	37
6"	12"	18"	24"	36"	48"	Custom Len.	
$65.38	$65.68	$66.00	$66.32	$66.96	$67.63	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3959				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	38
6"	12"	18"	24"	36"	48"	Custom Len.	
$58.53	$62.04	$62.62	$63.21	$64.37	$61.68	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3051				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	39
6"	12"	18"	24"	36"	48"	Custom Len.	
$55.94	$57.28	$55.26	$60.02	$58.91	$65.66	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3553				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	40
6"	12"	18"	24"	36"	48"	Custom Len.	
$59.47	$55.57	$57.16	$64.55	$61.93	$71.60	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3835				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	41
5"	6"	12"	18"	24"	36"	Custom Len.	
$60.55	$58.86	$60.54	$62.26	$59.22	$62.42	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3924				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	42
6"	12"	18"	24"	36"	48"	Custom Len.	
$69.24	$73.20	$71.60	$81.33	$83.10	$90.76	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

PE-P086EAM Coax, 50 Ohm

Part No. PE3CA1042				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.104" dia.			43
12"	24"	36"	100"	50CM	100CM	Custom Len.	
$68.78	$82.25	$107.18	Call	Call	$122.67	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE3799				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	44
6"	12"	18"	24"	36"	48"	Custom Len.	
$60.55	$65.23	$69.98	$79.67	$90.20	$93.52	See Web	

RG55B/U Coax, 53 Ohm

Part No. PE3940				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	45
6"	12"	18"	24"	36"	48"	Custom Len.	
$54.61	$54.61	$55.86	$57.09	$59.56	$62.02	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3871				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	46
6"	12"	18"	24"	36"	48"	Custom Len.	
$70.24	$70.77	$71.23	$71.77	$72.74	$73.75	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE3967				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	47
6"	12"	18"	24"	36"	48"	Custom Len.	
$63.63	$63.63	$64.95	$66.23	$68.82	$77.31	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE3806				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	48
6"	12"	18"	24"	36"	48"	Custom Len.	
$70.51	$71.23	$71.94	$72.68	$74.14	$75.58	See Web	

Standard Semi-Rigid Cable Assemblies

PE-020SR Coax, 50 Ohm

Part No. PE34241				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					85 dB/100ft	2.9 W	49
6"	12"	18"	24"	36"	48"	Custom Len.	
$147.87	$157.44	$166.93	$176.51	$195.56	$214.63	See Web	

PE-034SR Coax, 50 Ohm

Part No. PE34243				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					60 dB/100ft	10 W	50
6"	12"	18"	24"	36"	48"	Custom Len.	
$151.63	$158.29	$164.97	$171.62	$184.95	$198.31	See Web	

PE-047SR Coax, 50 Ohm

Part No. PE3531				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	51
6"	12"	18"	24"	36"	48"	Custom Len.	
$109.27	$114.68	$120.07	$125.43	$136.23	$146.95	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE3382				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	52
6"	12"	18"	24"	36"	48"	Custom Len.	
$108.69	$113.45	$118.19	$123.02	$132.51	$142.09	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34252				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	53
6"	12"	18"	24"	36"	48"	Custom Len.	
$69.02	$67.68	$72.85	$78.02	$88.37	$98.73	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34254				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	54
6"	12"	18"	24"	36"	48"	Custom Len.	
$64.37	$64.30	$74.68	$73.48	$82.71	$91.89	See Web	

RG401/U Coax, 50 Ohm

Part No. PE34256				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	55
6"	12"	18"	24"	36"	48"	Custom Len.	
$124.31	$135.82	$147.41	$158.92	$182.03	$205.11	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3825				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	56
6"	12"	18"	24"	36"	48"	Custom Len.	
$66.28	$65.25	$69.27	$73.27	$81.32	$89.34	See Web	
Part No. PE3C2892				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	57
6"	12"	18"	24"	36"	48"	Custom Len.	
$49.79	$49.79	$61.01	$64.91	$72.71	$80.49	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3826				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	58
6"	12"	18"	24"	36"	48"	Custom Len.	
$64.88	$71.37	$75.45	$79.55	$79.99	$87.55	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34247				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	59
6"	12"	18"	24"	36"	48"	Custom Len.	
$139.79	$139.79	$149.62	$159.45	$179.12	$198.80	See Web	

SMA MALE TO REVERSE POLARITY SMA MALE

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE37900				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		60
12"	24"	36"	48"	60"	-	Custom Len.	
$55.07	$56.53	$54.13	$54.96	$56.29	-	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3W00906				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		61
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.04	$64.08	$65.11	$66.15	$67.18	$63.70	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE34116				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	62
12"	24"	36"	48"	60"	72"	Custom Len.	
$65.55	$66.44	$62.30	$63.11	$63.92	$64.73	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE34614				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	63
12"	24"	36"	48"	60"	72"	Custom Len.	
$57.41	$63.70	$70.00	$76.32	$82.61	$88.92	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE34331				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	64
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.21	$56.25	$56.73	$57.19	$57.68	$58.16	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE35208				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	65
12"	24"	36"	48"	60"	72"	Custom Len.	
$79.14	$80.30	$74.08	$75.12	$76.18	$77.24	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE35210				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	66
12"	24"	36"	48"	60"	72"	Custom Len.	
$57.75	$60.19	$62.63	$65.07	$67.52	$69.96	See Web	

RG223/U Coax, 50 Ohm

Part No. PE34398				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	67
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.77	$56.48	$59.65	$62.84	$66.03	$73.93	See Web	

RG316/U Coax, 50 Ohm

Part No. PE35212				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	68
12"	24"	36"	48"	60"	72"	Custom Len.	
$58.83	$62.27	$65.70	$64.37	$67.67	$70.97	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE36963				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	69
12"	24"	36"	48"	60"	-	Custom Len.	
$63.23	$61.74	$70.09	$68.14	$71.34	-	See Web	

SMA MALE TO REVERSE POLARITY SMA MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W07225				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	70
12"	24"	36"	48"	60"	50CM	Custom Len.	
$91.39	$92.01	$92.63	$93.24	$93.86	$91.78	See Web	

SMA MALE TO REVERSE THREAD SMA MALE

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE35351				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	71
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.19	$57.00	$57.77	$58.56	$59.37	$60.21	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE35355				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	72
12"	24"	36"	48"	60"	72"	Custom Len.	
$58.35	$64.44	$70.57	$76.65	$82.79	$88.85	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

RG174A/U Coax, 50 Ohm

Part No. PE35359				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	73
12"	24"	36"	48"	60"	72"	Custom Len.	
$57.90	$58.35	$58.90	$59.37	$59.88	$60.33	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE35363				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	74
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.75	$67.79	$68.85	$69.91	$70.97	$72.03	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE35367				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	75
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.75	$62.12	$64.44	$66.81	$69.20	$71.50	See Web	

RG223/U Coax, 50 Ohm

Part No. PE35371				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	76
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.89	$63.08	$66.26	$69.44	$72.63	$75.83	See Web	

RG316/U Coax, 50 Ohm

Part No. PE35375				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	77
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.73	$64.03	$67.34	$70.64	$73.93	$77.24	See Web	

SMA MALE TO SMB PLUG

Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE34764				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	78
12"	24"	36"	48"	60"	-	Custom Len.	
$66.17	$78.91	$91.66	$104.40	$115.53	-	See Web	

Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm

Part No. PE34455				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.101" dia.			79
6"	12"	18"	24"	36"	48"	Custom Len.	
$57.32	$60.75	$61.22	$65.11	$72.92	$80.70	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3172				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	80
6"	12"	18"	24"	36"	48"	Custom Len.	
$56.59	$61.12	$57.00	$62.02	$62.90	$59.01	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3181				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		81
6"	12"	18"	24"	36"	48"	Custom Len.	
$54.90	$54.90	$61.54	$61.22	$71.57	$73.81	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3908				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	82
6"	12"	18"	24"	36"	48"	Custom Len.	
$51.71	$52.03	$52.35	$49.58	$53.32	$54.00	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3548				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	83
6"	12"	18"	24"	36"	48"	Custom Len.	
$67.58	$68.15	$63.63	$64.17	$70.49	$66.26	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3755				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	84
6"	12"	18"	24"	36"	48"	Custom Len.	
$52.04	$52.04	$53.28	$54.50	$56.46	$58.89	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE3722				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	85
6"	12"	18"	24"	36"	48"	Custom Len.	
$46.21	$46.21	$48.12	$50.00	$53.77	$57.03	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE34448				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	86
6"	12"	18"	24"	36"	48"	Custom Len.	
$63.54	$63.54	$64.28	$65.03	$66.53	$68.06	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3187				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	87
6"	12"	18"	24"	36"	48"	Custom Len.	
$52.27	$54.89	$53.88	$58.32	$58.17	$65.38	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3810				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	88
6"	12"	18"	24"	36"	48"	Custom Len.	
$52.62	$54.31	$55.52	$57.22	$60.67	$64.30	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE33657				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	89
6"	12"	18"	24"	36"	48"	Custom Len.	
$54.46	$57.72	$59.44	$61.17	$64.58	$68.23	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34452				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	90
6"	12"	18"	24"	36"	48"	Custom Len.	
$64.95	$71.43	$68.77	$72.60	$87.69	$87.93	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE35527				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	91
12"	24"	36"	48"	60"	-	Custom Len.	
$58.18	$70.99	$73.27	$80.84	$88.38	-	See Web	

SMA MALE TO SMB PLUG RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE3W00416				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.			92
12"	24"	36"	48"	60"	50CM	Custom Len.	
$36.83	$38.25	$39.68	$41.11	$42.54	$37.74	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W04476				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	93
12"	24"	36"	48"	60"	50CM	Custom Len.	
$45.80	$46.42	$47.04	$47.66	$48.28	$46.18	See Web	

SMA MALE TO SMB JACK

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W03014				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	94
12"	24"	36"	48"	60"	50CM	Custom Len.	
$43.56	$47.20	$50.84	$54.48	$57.60	$45.89	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3W05361				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	95
12"	24"	36"	48"	60"	50CM	Custom Len.	
$71.74	$75.30	$78.88	$82.44	$86.03	$74.03	See Web	

SMA MALE TO SMC PLUG

Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm

Part No. PE34460				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.101" dia.			96
6"	12"	14"	18"	24"	36"	Custom Len.	
$48.73	$52.59	Call	$55.87	$59.62	$67.13	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3210				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	97
6"	12"	18"	24"	36"	48"	Custom Len.	
$60.46	$60.46	$60.87	$61.28	$62.09	$62.89	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3944				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	98
6"	12"	18"	24"	36"	48"	Custom Len.	
$56.54	$56.54	$56.78	$57.03	$57.50	$57.98	See Web	
Part No. PE3W07493				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	99
12"	24"	36"	48"	60"	50CM	Custom Len.	
$45.03	$45.65	$46.28	$46.90	$47.52	$45.41	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3561				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	1
6"	12"	18"	24"	36"	48"	Custom Len.	
$58.35	$58.90	$59.43	$59.94	$61.00	$62.05	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

RG188A/U Coax, 50 Ohm

Part No. PE3736				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	2
6"	12"	18"	24"	36"	48"	Custom Len.	
$46.13	$47.31	$48.51	$49.65	$52.04	$54.45	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE34458				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	3
6"	12"	18"	24"	36"	48"	Custom Len.	
$51.04	$51.04	$52.91	$54.30	$58.04	$61.78	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE34450				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	4
6"	12"	18"	24"	36"	48"	Custom Len.	
$64.04	$64.04	$64.79	$65.56	$67.05	$68.56	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3226				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	5
6"	12"	18"	24"	36"	48"	Custom Len.	
$56.49	$56.49	$58.08	$59.67	$62.86	$66.04	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3809				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	6
6"	12"	18"	24"	36"	48"	Custom Len.	
$53.09	$53.09	$54.18	$60.24	$58.94	$62.12	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34456				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	7
6"	12"	18"	24"	36"	48"	Custom Len.	
$46.56	$46.56	$48.18	$52.83	$55.78	$55.73	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34454				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	8
6"	12"	18"	24"	36"	48"	Custom Len.	
$60.55	$64.37	$68.19	$72.11	$79.80	$87.53	See Web	

SMA MALE TO SMP FEMALE

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE36164				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	9
12"	24"	36"	48"	60"	72"	Custom Len.	
$99.86	$107.28	$108.87	$125.41	$124.85	$132.85	See Web	

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE36166				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	10
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.73	$76.88	$85.05	$93.69	$96.29	$103.83	See Web	

SMA MALE TO SMP FEMALE RIGHT ANGLE

Flexible Cable Assemblies

PE-P047 Coax, 50 Ohm

Part No. PE3C4968				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					35 dB/100ft	43 W	11
12"	24"	36"	48"	60"	50CM	Custom Len.	
$108.02	$116.95	$121.41	$130.35	$139.29	$109.27	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W06701				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	12
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.83	$84.67	$94.52	$104.35	$112.62	$81.13	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C3028				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	13
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.13	$60.07	$63.40	$66.75	$70.06	$58.88	See Web	
Part No. PE3W05274				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	14
12"	24"	36"	48"	60"	50CM	Custom Len.	
$51.13	$66.17	$69.77	$73.38	$77.00	$64.87	See Web	

SMA MALE TO SSMA MALE

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE3W01283				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.			15
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.34	$55.26	$56.66	$58.09	$59.50	$54.74	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE35430				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	16
6"	12"	18"	24"	36"	48"	Custom Len.	
$69.11	$63.11	$63.35	$63.61	$64.08	$64.55	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3058				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	17
6"	12"	18"	24"	36"	48"	Custom Len.	
$76.57	$72.76	$73.29	$73.82	$79.46	$80.69	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE37401				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	19
12"	24"	36"	48"	60"	-	Custom Len.	
$70.17	$73.61	$71.36	$74.58	$77.76	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3669				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	18
6"	12"	18"	24"	36"	48"	Custom Len.	
$69.79	$71.46	$73.19	$69.34	$72.52	$75.69	See Web	

SMA MALE TO SSMC PLUG

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4422				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		20
6"	12"	18"	24"	36"	48"	Custom Len.	
$54.56	$54.97	$50.83	$51.25	$56.63	$52.87	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4444				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	21
6"	12"	18"	24"	36"	48"	Custom Len.	
$67.85	$72.41	$77.10	$81.78	$82.35	$90.63	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4391				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	22
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.01	$78.70	$79.67	$79.95	$81.19	$82.43	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE3W06410				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	23
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.55	$74.18	$75.82	$77.44	$79.08	$73.59	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4437				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	25
6"	12"	18"	24"	36"	48"	Custom Len.	
$63.67	$65.33	$60.96	$68.78	$65.61	$75.85	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4405				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	24
6"	12"	18"	24"	36"	48"	Custom Len.	
$61.19	$62.73	$68.22	$65.81	$68.90	$71.97	See Web	

SMA MALE TO SSMC PLUG RIGHT ANGLE

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4423				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		26
6"	12"	18"	24"	36"	48"	Custom Len.	
$49.00	$49.41	$49.83	$47.42	$48.25	$51.99	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4484				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	27
6"	12"	18"	24"	36"	48"	Custom Len.	
$58.27	$68.65	$66.54	$70.68	$87.43	$87.23	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4463				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
6"	12"	18"	24"	36"	48"	Custom Len.
$61.77	$66.03	$62.80	$63.31	$64.34	$65.36	See Web

28

RG316/U Coax, 50 Ohm

Part No. PE3C4406				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
6"	12"	18"	24"	36"	48"	Custom Len.
$55.10	$56.58	$58.07	$59.52	$62.49	$65.44	See Web

29

RG316-DS Coax, 50 Ohm

Part No. PE3C4471				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W
6"	12"	18"	24"	36"	48"	Custom Len.
$52.32	$58.76	$60.46	$56.52	$59.63	$62.73	See Web

30

SMA MALE TO SSMC JACK

Standard Flexible Cable Assemblies

RG316-DS Coax, 50 Ohm

Part No. PE3W04458				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$57.15	$60.71	$64.29	$67.87	$71.44	$59.44	See Web

31

SMA MALE TO SSMC JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4445				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	18"	24"	36"	48"	Custom Len.
$54.18	$58.31	$62.46	$66.58	$74.87	$83.14	See Web

32

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4392				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
6"	12"	18"	24"	36"	48"	Custom Len.
$66.66	$71.20	$67.68	$68.20	$69.22	$70.24	See Web

33

SMA MALE TO TNC MALE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE36058				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W
12"	24"	36"	48"	60"	-	Custom Len.
$42.91	$43.77	$44.64	$42.11	$42.90	-	See Web

34

PE-C240 Coax, 50 Ohm

Part No. PE38642				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W
12"	24"	36"	48"	60"	-	Custom Len.
$52.70	$53.77	$54.53	$57.58	$60.68	-	See Web

35

LMR-195 Coax, 50 Ohm

Part No. PE3C4164				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft	
12"	24"	36"	48"	60"	-	Custom Len.
$61.75	$59.06	$59.85	$60.66	$61.46	-	See Web

36

Part No. PE3C4535				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$47.26	$47.96	$48.67	$49.38	$50.09	$46.99	See Web

37

PE-P142LL Coax, 50 Ohm

Part No. PE3C0847				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$156.54	$174.15	$191.76	$209.35	$226.96	$167.82	See Web

38

PE-P160LL Coax, 50 Ohm

Part No. PE3C5258				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$222.74	$245.21	$267.66	$290.11	$312.56	$237.13	See Web

39

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0129				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.		
12"	18"	24"	36"	48"	60"	Custom Len.
$398.21	$407.39	$416.58	$434.97	$453.35	$471.74	See Web

40

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0183				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
8"	12"	18"	24"	30"	36"	Custom Len.
$383.46	$388.77	$396.74	$404.70	$412.68	$420.65	See Web

41

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0227				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.3" dia.		
12"	18"	24"	36"	48"	60"	Custom Len.
$435.24	$450.59	$465.92	$496.60	$527.30	$557.98	See Web

42

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE338				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$298.59	$326.70	Call	$382.96	$411.06	$316.61	See Web

43

Part No. PE3C3242				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$236.63	$263.97	$291.28	$318.61	$345.94	$254.14	See Web

44

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34412				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W
6"	12"	18"	24"	36"	48"	Custom Len.
$87.06	$90.96	$94.92	$98.80	$106.67	$112.94	See Web

45

PE-SR401FL Coax, 50 Ohm

Part No. PE34422				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W
6"	12"	18"	24"	36"	48"	Custom Len.
$168.38	$176.98	$175.31	$183.65	$200.34	$217.04	See Web

46

PE-SR402FL Coax, 50 Ohm

Part No. PE33928				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W
6"	12"	18"	24"	36"	48"	Custom Len.
$86.47	$86.47	$91.07	$95.66	$104.84	$112.44	See Web

47

PE-SR405FL Coax, 50 Ohm

Part No. PE34416				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W
6"	12"	18"	24"	36"	48"	Custom Len.
$75.17	$75.21	$80.93	$86.61	$98.03	$107.94	See Web

48

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE33669				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W
12"	24"	36"	48"	60"	-	Custom Len.
$122.10	$124.89	$136.08	$130.56	$133.42	-	See Web

49

RG58C/U Coax, 50 Ohm

Part No. PE3154				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	72"	Custom Len.
$46.78	$47.68	$48.58	$49.55	$50.46	$51.39	See Web

50

RG141A/U Coax, 50 Ohm

Part No. PE37580				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W
12"	24"	36"	48"	60"	-	Custom Len.
$53.51	$59.55	$66.10	$72.61	$79.20	-	See Web

51

RG142B/U Coax, 50 Ohm

Part No. PE3664				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W
12"	24"	36"	48"	60"	72"	Custom Len.
$50.45	$59.67	$66.36	$73.43	$80.24	$81.50	See Web

52

RG174A/U Coax, 50 Ohm

Part No. PE3178				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W
12"	24"	36"	48"	60"	72"	Custom Len.
$62.07	$59.04	$63.34	$59.99	$60.45	$65.30	See Web

53

RG178B/U Coax, 50 Ohm

Part No. PE34248				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W
12"	24"	36"	48"	60"	72"	Custom Len.
$77.25	$78.41	$74.97	$76.04	$77.07	$78.13	See Web

54

RG188A/U Coax, 50 Ohm

Part No. PE33361				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$60.57	$63.01	$65.44	$67.89	$70.33	$72.76	See Web

55

RG213/U Coax, 50 Ohm

Part No. PE33673				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W
12"	24"	36"	48"	60"	72"	Custom Len.
$135.92	$137.71	$139.52	$141.31	$143.12	$144.92	See Web

56

Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

RG214/U Coax, 50 Ohm

Part No. PE3176				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	57
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	170 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$151.58	$159.51	$167.48	$175.40	$183.34	$191.29	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3535				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	58
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$51.13	$54.09	$57.50	$61.14	$60.56	$68.12	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3174				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	59
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.52	$69.97	$73.41	$77.04	$80.54	$84.04	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34246				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	60
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.19	$58.40	$61.60	$64.79	$67.99	$78.23	See Web	

RG393/U Coax, 50 Ohm

Part No. PE34253				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	61
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$151.91	$168.82	$185.68	$202.58	$219.51	$236.40	See Web	

RG400/U Coax, 50 Ohm

Part No. PE33948				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	62
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.58	$71.72	$79.84	$88.45	$96.73	$98.30	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE33396				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	63
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$53.13	$62.39	$76.85	$81.83	$98.73	-	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3CA1064				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	64
1 piece price shown. See web or call for volume pricing.				0.24" dia.			
12"	24"	36"	48"	60"	72"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

LMR-400 Coax, 50 Ohm

Part No. PE3CA1080				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	65
1 piece price shown. See web or call for volume pricing.				0.405" dia.			
12"	24"	36"	48"	60"	72"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0026				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	66
1 piece price shown. See web or call for volume pricing.				0.195" dia.			
12"	18"	24"	30"	36"	48"	Custom Len.	
$203.73	$206.69	$209.65	$212.59	$215.55	$221.47	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0054				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	67
1 piece price shown. See web or call for volume pricing.				0.212" dia.			
12"	18"	24"	30"	36"	48"	Custom Len.	
$208.38	$213.68	$218.97	$224.25	$229.56	$240.12	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0082				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	68
1 piece price shown. See web or call for volume pricing.				0.195" dia.			
12"	18"	24"	30"	36"	48"	Custom Len.	
$205.34	$209.11	$212.87	$216.63	$220.39	$227.91	See Web	

M17/113-RG316-27478 Coax, 50 Ohm

Part No. PE3M0096				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	69
1 piece price shown. See web or call for volume pricing.				0.098" dia.			
6"	8"	12"	16"	18"	24"	Custom Len.	
$195.98	$196.33	$197.06	$197.79	$198.15	$199.23	See Web	

M17/119-RG174-0XDS2 Coax, 50 Ohm

Part No. PE3M0111				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	70
1 piece price shown. See web or call for volume pricing.				0.11" dia.			
6"	8"	12"	16"	18"	24"	Custom Len.	
$195.32	$195.44	$195.73	$196.01	$196.16	$196.58	See Web	

M17/28-RG058-0XDS2 Coax, 50 Ohm

Part No. PE3M0122				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	71
1 piece price shown. See web or call for volume pricing.				0.195" dia.			
12"	18"	24"	30"	36"	48"	Custom Len.	
$316.07	$316.70	$317.36	$318.00	$318.66	$319.96	See Web	

RG55B/U Coax, 53 Ohm

Part No. PE34250				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	72
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$47.29	$49.76	$52.26	$54.24	$56.72	$59.17	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE36848				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	73
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$53.98	$54.53	$57.90	$56.63	$57.70	-	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE34255				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	74
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.86	$63.47	$66.08	$68.66	$71.26	$73.86	See Web	

Standard Semi-Rigid Cable Assemblies

PE-SR047AL Coax, 50 Ohm

Part No. PE34410				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	75
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$87.99	$92.81	$97.62	$102.51	$110.58	$120.16	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34406				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	76
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$76.78	$82.21	$82.58	$87.60	$97.62	$107.65	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34414				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	77
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$68.39	$73.01	$77.62	$82.18	$91.43	$100.59	See Web	

RG401/U Coax, 50 Ohm

Part No. PE34418				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	78
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$162.34	$174.27	$175.92	$187.50	$210.60	$233.62	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3089				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	79
1 piece price shown. See web or call for volume pricing.					11.1 dB/100ft	450 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$78.35	$78.35	$82.35	$86.37	$94.41	$102.44	See Web	

RG405/U Coax, 50 Ohm

Part No. PE33420				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	80
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$76.78	$76.78	$85.48	$84.35	$91.90	$99.44	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34420				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	81
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$174.57	$170.00	$179.83	$189.66	$209.33	$229.01	See Web	

PE-047SR Coax, 50 Ohm

Part No. PE34408				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	82
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$88.59	$94.05	$99.53	$104.95	$114.29	$125.04	See Web	

SMA MALE TO TNC MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C0780				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	83
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$243.96	$261.57	$279.15	$296.76	$314.36	$255.24	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5259				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	84
1 piece price shown. See web or call for volume pricing.				0.16" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$286.46	$308.91	$331.37	$353.83	$376.28	$300.85	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0131				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	85
1 piece price shown. See web or call for volume pricing.				0.195" dia.			
12"	18"	24"	36"	48"	60"	Custom Len.	
$513.86	$523.05	$532.24	$550.62	$569.00	$587.40	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0185				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	86
1 piece price shown. See web or call for volume pricing.				0.16" dia.			
8"	12"	18"	24"	30"	36"	Custom Len.	
$475.62	$480.94	$488.90	$496.87	$504.85	$512.81	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0228				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	87
1 piece price shown. See web or call for volume pricing.				0.3" dia.			
12"	18"	24"	36"	48"	60"	Custom Len.	
$591.67	$607.01	$622.36	$653.04	$683.72	$714.41	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W07181				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	88
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.43	$63.77	$73.61	$83.46	$93.31	$60.24	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

SMA MALE TO TNC FEMALE

Flexible Cable Assemblies

LMR-195-FR Coax, 50 Ohm

Part No. PE3C5480				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		89
12"	24"	36"	48"	60"	50CM	Custom Len.	
$43.56	$42.22	$43.34	$44.46	$45.57	$41.81	See Web	

SMA MALE TO TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3W02172				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		90
12"	24"	36"	48"	60"	50CM	Custom Len.	
$43.19	$43.88	$44.22	$44.90	$45.59	$43.28	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE3C2449				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		91
12"	24"	36"	48"	60"	50CM	Custom Len.	
$193.80	$211.41	$229.01	$246.62	$264.22	$205.08	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0130				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			92
12"	18"	24"	36"	48"	60"	Custom Len.	
$483.70	$492.88	$502.07	$520.46	$538.84	$557.22	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0184				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			93
8"	12"	18"	24"	30"	36"	Custom Len.	
$471.35	$476.67	$484.63	$492.60	$500.58	$508.55	See Web	

Precision Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39475				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	94
6"	9"	12"	18"	24"	-	Custom Len.	
$57.24	$54.22	$57.24	$63.63	Call	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39489				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	95
6"	9"	12"	18"	24"	-	Custom Len.	
$53.12	$50.10	$53.12	Call	$62.49	-	See Web	

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39483				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	400 W	96
6"	9"	12"	18"	24"	-	Custom Len.	
$53.55	$50.52	$53.55	$57.66	$62.23	-	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39497				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	97
6"	9"	12"	18"	24"	-	Custom Len.	
$60.19	$56.78	$60.19	Call	$70.06	-	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W05224				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	98
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.59	$63.20	$66.80	$70.41	$74.03	$61.90	See Web	

SMA MALE TO REVERSE POLARITY TNC MALE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE37120				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	99
12"	24"	36"	48"	60"	-	Custom Len.	
$47.99	$44.42	$45.22	$46.00	$51.53	-	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE34853				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	1
12"	24"	36"	48"	60"	72"	Custom Len.	
$50.95	$51.76	$52.59	$53.40	$54.21	$54.53	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE34854				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	2
12"	24"	36"	48"	60"	72"	Custom Len.	
$52.04	$62.37	$69.06	$70.47	$82.94	$83.09	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE35242				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	3
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.83	$71.88	$72.95	$74.02	$75.04	$76.10	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE35244				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	4
12"	24"	36"	48"	60"	72"	Custom Len.	
$57.84	$60.15	$62.52	$64.83	$67.21	$69.59	See Web	

RG223/U Coax, 50 Ohm

Part No. PE34397				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	5
12"	24"	36"	48"	60"	72"	Custom Len.	
$48.83	$52.04	$54.75	$57.94	$61.13	$64.32	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34396				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	6
12"	24"	36"	48"	60"	72"	Custom Len.	
$58.77	$66.89	$70.33	$68.65	$71.94	$75.26	See Web	

RG400/U Coax, 50 Ohm

Part No. PE35246				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	7
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.06	$62.77	$70.51	$78.23	$85.93	$93.67	See Web	

SMA MALE TO HMCX32 1.2 PLUG

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1030				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			8
3"	6"	12"	-	-	-	Custom Len.	
$12.80	$14.76	$14.76	-	-	-	See Web	

SMA MALE TO UMCX PLUG

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38881				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.			9
3"	6"	9"	12"	18"	24"	Custom Len.	
$71.74	$73.62	$75.51	$77.39	$81.27	$85.15	See Web	

SMA MALE TO UMCX 2.1 PLUG

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1028				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			10
3"	6"	12"	18"	-	-	Custom Len.	
$17.35	$16.63	$14.76	Call	-	-	See Web	

SMA MALE TO UMCX 2.5 PLUG

Standard Flexible Cable Assemblies

RG178-DS Coax, 50 Ohm

Part No. PE3CA1027				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.086" dia.			11
3"	6"	9"	12"	18"	-	Custom Len.	
$13.00	$22.89	$12.80	$16.03	Call	-	See Web	

PE-81mm Coax, 50 Ohm

Part No. PE3CA1023				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			12
3"	6"	12"	-	-	-	Custom Len.	
$12.93	$12.80	$16.63	-	-	-	See Web	

PE-113mm Coax, 50 Ohm

Part No. PE3CA1024				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.044" dia.			13
3"	6"	25CM	12"	18"	-	Custom Len.	
$16.10	$16.10	Call	$16.10	$17.49	-	See Web	

Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

PE-137mm Coax, 50 Ohm

Part No. PE3CA1025				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.053" dia.			14
3"	6"	12"	-	-	-	Custom Len.	
$16.63	$14.76	$14.48	-	-	-	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3CA1026					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.07" dia.			15
3"	4"	6"	9"	12"	44CM	Custom Len.		
Call	Call	$12.80	$14.76	$14.76	Call	See Web		

SMA MALE TO WMCX 1.6 PLUG

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1029				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			16
3"	6"	12"	-	-	-	Custom Len.	
$14.76	$14.76	$14.76	-	-	-	See Web	

SMA MALE TO NEX10 MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6258				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	17
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.92	$67.05	$73.19	$79.32	$85.45	$64.84	See Web	

REVERSE POLARITY SMA MALE TO BNC MALE

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE35207				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	18
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.47	$60.82	$61.72	$57.91	$58.72	$59.52	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE35209				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	19
12"	24"	36"	48"	60"	72"	Custom Len.	
$51.46	$57.30	$63.61	$75.51	$76.19	$82.52	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3332				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	20
12"	24"	36"	48"	60"	72"	Custom Len.	
$47.78	$53.20	$48.67	$49.19	$49.64	$50.16	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE35213				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	21
12"	24"	36"	48"	60"	72"	Custom Len.	
$75.58	$76.65	$77.69	$78.75	$84.87	$80.86	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3C3412				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	22
12"	24"	36"	48"	60"	72"	Custom Len.	
$49.59	$51.82	$54.12	$55.92	$58.14	$60.42	See Web	

RG223/U Coax, 50 Ohm

Part No. PE35217				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	23
12"	24"	36"	48"	60"	72"	Custom Len.	
$51.19	$51.52	$57.58	$57.42	$60.60	$63.80	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C3413				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	24
12"	24"	36"	48"	60"	72"	Custom Len.	
$50.47	$58.43	$61.88	$59.52	$62.71	$65.88	See Web	

REVERSE POLARITY SMA MALE TO MCX PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C0481				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	25
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.81	$67.26	$66.54	$69.72	$77.83	$76.08	See Web	

REVERSE POLARITY SMA MALE TO N MALE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE36072				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	26
12"	24"	36"	48"	60"	-	Custom Len.	
$53.84	$54.12	$54.90	$55.70	$56.49	-	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE34727				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	27
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.48	$60.29	$66.03	$61.91	$62.72	$63.54	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE34361				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	28
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.94	$65.66	$76.29	$83.37	$84.57	$96.99	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE35221				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	29
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.96	$66.48	$61.92	$62.41	$62.87	$63.35	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE35223				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	30
12"	24"	36"	48"	60"	72"	Custom Len.	
$81.06	$87.09	$83.19	$84.23	$85.28	$86.34	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE35225				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	31
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.73	$65.38	$67.83	$70.26	$72.69	$75.15	See Web	

RG223/U Coax, 50 Ohm

Part No. PE35227				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	32
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.27	$59.46	$62.66	$70.11	$73.61	$72.20	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34770				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	33
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.73	$67.07	$70.26	$73.44	$76.60	$79.77	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34323				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	34
12"	24"	36"	48"	60"	-	Custom Len.	
$67.44	$71.28	$83.72	$86.61	$100.59	-	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE35508				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	35
12"	24"	36"	48"	60"	-	Custom Len.	
$68.23	$77.97	$87.70	$97.43	$107.17	-	See Web	

REVERSE POLARITY SMA MALE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3W02336				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	80 W	36
12"	24"	36"	48"	60"	50CM	Custom Len.	
$61.78	$62.63	$63.49	$64.36	$65.22	$62.33	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE34575				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	37
12"	24"	36"	48"	60"	-	Custom Len.	
$64.19	$70.49	$76.77	$83.10	$89.39	-	See Web	

REVERSE POLARITY SMA MALE TO REVERSE POLARITY SMA MALE

Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE34750				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	38
12"	18"	24"	36"	48"	60"	Custom Len.	
$61.21	$64.55	$67.89	$74.58	$76.09	$82.21	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

REVERSE POLARITY SMA MALE TO REVERSE POLARITY SMA FEMALE

Standard Flexible Cable Assemblies

RG141A/U Coax, 50 Ohm

Part No. PE3C5980				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W	39
12"	24"	36"	48"	60"	50CM	Custom Len.	
$85.55	$101.03	$107.62	$115.61	$123.62	$98.11	See Web	

REVERSE POLARITY SMA MALE TO TNC MALE

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE35214				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	40
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.61	$61.50	$57.74	$58.55	$59.37	$60.17	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE35216				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	41
12"	24"	36"	48"	60"	72"	Custom Len.	
$57.82	$64.14	$70.43	$76.74	$83.02	$89.34	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE35218				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	42
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.86	$61.34	$61.86	$62.33	$62.77	$63.30	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE35220				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	43
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.29	$87.28	$80.40	$81.45	$82.53	$83.56	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE35222				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	44
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.72	$65.10	$67.40	$69.77	$72.11	$74.45	See Web	

RG223/U Coax, 50 Ohm

Part No. PE35224				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	45
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.77	$57.96	$61.15	$64.34	$67.52	$70.70	See Web	

RG316/U Coax, 50 Ohm

Part No. PE35226				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	46
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.74	$71.90	$75.08	$78.26	$86.87	$84.61	See Web	

REVERSE THREAD SMA MALE TO REVERSE THREAD SMA MALE

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE35349				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	47
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.67	$68.53	$69.32	$70.11	$70.91	$71.71	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE35353				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	48
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.83	$76.90	$83.02	$89.10	$95.19	$101.32	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE35357				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	49
12"	24"	36"	48"	60"	72"	Custom Len.	
$76.13	$76.63	$77.10	$77.57	$78.05	$78.53	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE35361				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	50
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.35	$73.41	$74.45	$75.53	$76.58	$85.53	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE35365				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	51
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.68	$76.05	$78.37	$80.75	$83.02	$85.42	See Web	

RG223/U Coax, 50 Ohm

Part No. PE35369				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	52
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.38	$76.58	$79.76	$82.94	$86.12	$89.33	See Web	

RG316/U Coax, 50 Ohm

Part No. PE35373				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	53
12"	24"	36"	48"	60"	72"	Custom Len.	
$74.61	$77.89	$81.19	$84.49	$87.79	$91.10	See Web	

SMA MALE RIGHT ANGLE TO SMA MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0025				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			54
12"	18"	24"	30"	36"	48"	Custom Len.	
$310.29	$313.24	$316.20	$319.15	$322.11	$328.04	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0053				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			55
12"	18"	24"	30"	36"	48"	Custom Len.	
$314.95	$320.24	$325.53	$330.82	$336.12	$346.68	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0081				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			56
12"	18"	24"	30"	36"	48"	Custom Len.	
$311.90	$315.66	$319.43	$323.18	$326.95	$334.48	See Web	

M17/113-RG316-27478 Coax, 50 Ohm

Part No. PE3M0093				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.			57
6"	8"	12"	16"	18"	24"	Custom Len.	
$222.14	$222.50	$223.24	$223.94	$224.33	$225.41	See Web	

M17/119-RG174-0XDS2 Coax, 50 Ohm

Part No. PE3M0108				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.			58
6"	8"	12"	16"	18"	24"	Custom Len.	
$221.48	$221.61	$221.91	$222.17	$222.33	$222.75	See Web	

M17/28-RG058-0XDS2 Coax, 50 Ohm

Part No. PE3M0121				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			59
12"	18"	24"	30"	36"	48"	Custom Len.	
$218.78	$219.42	$220.08	$220.70	$221.37	$222.66	See Web	

SMA MALE RIGHT ANGLE TO SMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

M17/113-RG316-27478 Coax, 50 Ohm

Part No. PE3M0094				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.			60
6"	8"	12"	16"	18"	24"	Custom Len.	
$212.13	$212.48	$213.21	$213.94	$214.30	$215.39	See Web	

M17/119-RG174-0XDS2 Coax, 50 Ohm

Part No. PE3M0109				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.			61
6"	8"	12"	16"	18"	24"	Custom Len.	
$211.47	$211.61	$211.89	$212.17	$212.31	$212.73	See Web	

SMA MALE RIGHT ANGLE TO TNC MALE

Standard Flexible Cable Assemblies

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0027				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			62
12"	18"	24"	30"	36"	48"	Custom Len.	
$242.86	$245.81	$248.76	$251.71	$254.68	$260.59	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0055				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.212" dia.			63
12"	18"	24"	30"	36"	48"	Custom Len.	
$247.51	$252.79	$258.10	$263.38	$268.67	$279.25	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0083				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			64
12"	18"	24"	30"	36"	48"	Custom Len.	
$244.45	$248.21	$251.98	$255.75	$259.50	$267.03	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

M17/113-RG316-27478 Coax, 50 Ohm

Part No. PE3M0097				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.			65
6"	8"	12"	16"	18"	24"	Custom Len.	
$213.16	$213.53	$214.26	$214.96	$215.35	$216.43	See Web	

M17/119-RG174-0XDS2 Coax, 50 Ohm

Part No. PE3M0112				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.			66
6"	8"	12"	16"	18"	24"	Custom Len.	
$212.50	$212.64	$212.93	$213.20	$213.36	$213.77	See Web	

M17/28-RG058-0XDS2 Coax, 50 Ohm

Part No. PE3M0123				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			67
12"	18"	24"	30"	36"	48"	Custom Len.	
$250.30	$250.94	$251.59	$252.23	$252.89	$254.18	See Web	

SMA MALE RIGHT ANGLE TO BNC MALE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38093				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	68
12"	24"	36"	48"	60"	-	Custom Len.	
$50.49	$46.70	$47.50	$48.27	$54.04	-	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3850				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	69
6"	12"	18"	24"	36"	48"	Custom Len.	
$57.78	$57.78	$58.21	$64.46	$65.34	$60.23	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3780				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	70
6"	12"	18"	24"	36"	48"	Custom Len.	
$50.35	$50.60	$53.79	$56.46	$62.74	$69.06	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3448				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	71
6"	12"	18"	24"	36"	48"	Custom Len.	
$56.92	$57.22	$57.54	$57.85	$58.50	$58.32	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE33257				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	72
12"	24"	36"	48"	60"	-	Custom Len.	
$91.75	$92.92	$94.08	$95.30	$96.48	-	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3C3437				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	73
6"	12"	18"	24"	36"	48"	Custom Len.	
$56.95	$61.51	$58.18	$59.40	$67.00	$69.90	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3733				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	74
6"	12"	18"	24"	36"	48"	Custom Len.	
$65.87	$67.54	$63.00	$70.96	$74.38	$78.00	See Web	

RG303/U Coax, 50 Ohm

Part No. PE39138				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.17" dia.	14 dB/100ft	650 W	75
12"	24"	36"	48"	60"	-	Custom Len.	
$47.65	$56.16	$59.82	$66.12	$72.42	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C3350				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	76
6"	12"	18"	24"	36"	48"	Custom Len.	
$60.21	$65.03	$61.79	$68.47	$71.89	$75.53	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3642				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	77
6"	12"	18"	24"	36"	48"	Custom Len.	
$66.18	$68.82	$70.00	$73.83	$81.50	$89.15	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE33889				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	78
12"	24"	36"	48"	60"	-	Custom Len.	
$56.92	$66.66	$76.39	$86.11	$103.29	-	See Web	

SMA MALE RIGHT ANGLE TO BNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3681				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	79
12"	24"	36"	48"	60"	-	Custom Len.	
$72.61	$76.06	$74.87	$83.13	$81.20	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34957				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	80
12"	24"	36"	48"	60"	-	Custom Len.	
$84.10	$85.55	$93.20	$100.87	$107.03	-	See Web	

SMA MALE RIGHT ANGLE TO MCX PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W10654				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		81
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.56	$69.21	$72.86	$76.51	$80.16	$64.24	See Web	

Standard Semi-Rigid Cable Assemblies

PE-SR405AL Coax, 50 Ohm

Part No. PE3W02882				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	82
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.16	$69.32	$79.47	$89.62	$99.79	$65.67	See Web	

SMA MALE RIGHT ANGLE TO MCX JACK

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W02744				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	83
12"	24"	36"	48"	60"	50CM	Custom Len.	
$72.39	$75.71	$79.05	$82.38	$85.72	$74.50	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3W01114				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	84
12"	24"	36"	48"	60"	50CM	Custom Len.	
$64.07	$67.41	$70.73	$74.08	$77.41	$66.21	See Web	

SMA MALE RIGHT ANGLE TO MMCX PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36507				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	85
12"	24"	36"	48"	60"	-	Custom Len.	
$73.61	$74.23	$74.88	$75.55	$68.81	-	See Web	

SMA MALE RIGHT ANGLE TO N MALE

Low Loss Flexible Cable Assemblies

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0156				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			86
12"	18"	24"	36"	48"	60"	Custom Len.	
$497.76	$506.96	$516.15	$534.54	$552.91	$571.30	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0201				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			87
8"	12"	18"	24"	30"	36"	Custom Len.	
$484.14	$489.47	$497.43	$505.41	$513.38	$521.34	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0235				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			88
12"	18"	24"	36"	48"	60"	Custom Len.	
$574.91	$590.26	$605.61	$636.29	$666.97	$697.65	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3238				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		89
12"	24"	36"	48"	60"	50CM	Custom Len.	
$270.71	$298.01	$325.31	$352.62	$379.91	$288.22	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE3W00921				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	90
12"	24"	36"	48"	60"	50CM	Custom Len.	
$57.99	$64.48	$70.97	$77.45	$83.95	$62.15	See Web	

SMA MALE RIGHT ANGLE TO N MALE RIGHT ANGLE

Flexible Cable Assemblies

LMR-195-FR Coax, 50 Ohm

Part No. PE3W05298				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		91
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.01	$61.11	$62.19	$63.29	$64.39	$60.70	See Web	

Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3W00852				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		92
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.10	$58.90	$59.70	$60.51	$61.29	$58.59	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE3C1528				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		93
12"	24"	36"	48"	60"	50CM	Custom Len.	
$329.95	$347.56	$365.16	$382.77	$400.36	$341.23	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0158					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.195" dia.			94
12"	18"	24"	36"	48"	60"	Custom Len.		
$622.48	$631.67	$640.86	$659.24	$677.63	$696.01	See Web		

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0203				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			95
8"	12"	18"	24"	30"	36"	Custom Len.	
$590.46	$595.79	$603.74	$611.72	$619.68	$627.66	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0237					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.3" dia.			96
12"	18"	24"	36"	48"	60"	Custom Len.		
$732.05	$747.40	$751.48	$793.43	$827.49	$854.80	See Web		

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3249				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		97
12"	24"	36"	48"	60"	50CM	Custom Len.	
$489.56	$516.90	$544.22	$571.55	$598.87	$507.07	See Web	

SMA MALE RIGHT ANGLE TO N FEMALE

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3250				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		98
12"	24"	36"	48"	60"	50CM	Custom Len.	
$389.60	$416.91	$444.24	$471.57	$498.89	$407.08	See Web	

SMA MALE RIGHT ANGLE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C2985				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		99
12"	24"	36"	48"	60"	50CM	Custom Len.	
$279.81	$297.41	$315.01	$332.63	$350.21	$291.09	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0157					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.195" dia.			1
12"	18"	24"	36"	48"	60"	Custom Len.		
$592.32	$601.50	$610.69	$629.08	$647.46	$665.84	See Web		

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0202					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.16" dia.			2
8"	12"	18"	24"	30"	36"	Custom Len.		
$594.73	$600.04	$608.01	$615.98	$623.95	$631.92	See Web		

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0236					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					0.3" dia.			3
12"	18"	24"	36"	48"	60"	Custom Len.		
$656.95	$672.31	$687.64	$718.33	$749.01	$779.69	See Web		

Precision Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39456				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	4
6"	9"	12"	18"	24"	-	Custom Len.	
$59.44	Call	$59.44	$64.03	$68.62	-	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39470				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	5
6"	9"	12"	18"	24"	-	Custom Len.	
$60.93	Call	$60.93	$65.86	Call	-	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C3245				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		6
12"	24"	36"	48"	60"	50CM	Custom Len.	
$452.24	$479.55	$506.88	$534.20	$561.54	$469.72	See Web	

Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39448				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	7
6"	9"	12"	18"	24"	-	Custom Len.	
$72.55	$61.10	$72.55	$79.00	Call	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39462				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	8
6"	9"	12"	18"	24"	-	Custom Len.	
$68.28	$57.72	$68.28	Call	$78.15	-	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE34351				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	9
12"	24"	36"	48"	60"	-	Custom Len.	
$92.39	$86.03	$93.66	$86.98	$87.46	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE33014				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		10
12"	24"	36"	48"	60"	-	Custom Len.	
$83.22	$83.20	$86.37	$93.73	$92.72	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3179				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	11
12"	24"	36"	48"	60"	-	Custom Len.	
$85.31	$88.17	$101.58	$103.49	$109.59	-	See Web	

SMA MALE RIGHT ANGLE TO SMA MALE

Flexible Cable Assemblies

LMR-240 Coax, 50 Ohm

Part No. PE3C6658				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		12
12"	24"	36"	48"	60"	-	Custom Len.	
$53.47	$54.45	$54.91	$55.89	$56.87	-	See Web	

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE342				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		13
12"	24"	36"	48"	60"	50CM	Custom Len.	
$212.69	$230.29	$247.88	$265.49	$283.09	$223.96	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39431				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	14
6"	9"	12"	18"	24"	-	Custom Len.	
$46.74	$44.44	$46.74	$51.73	$56.19	-	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W06425				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		15
12"	24"	36"	48"	60"	50CM	Custom Len.	
$59.70	$63.29	$66.90	$70.52	$74.13	$62.01	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3W06660				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	16
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.29	$68.78	$72.43	$76.00	$79.59	$67.58	See Web	

SMA MALE RIGHT ANGLE TO SMA MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-C195 Coax, 50 Ohm

Part No. PE35347				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	17
12"	24"	36"	48"	60"	-	Custom Len.	
$60.65	$56.93	$57.72	$58.51	$59.30	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE38920				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	18
12"	24"	36"	48"	60"	-	Custom Len.	
$86.98	$85.15	$88.25	$90.79	$92.05	-	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE3C1425				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		19
12"	24"	36"	48"	60"	50CM	Custom Len.	
$306.65	$324.25	$341.86	$359.44	$377.05	$317.92	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5248				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			20
12"	24"	36"	48"	60"	50CM	Custom Len.	
$303.22	$325.68	$348.12	$370.58	$393.04	$317.61	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0152				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			21
12"	18"	24"	36"	48"	60"	Custom Len.	
$594.32	$603.50	$612.70	$631.08	$649.47	$667.85	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0197				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			22
8"	12"	18"	24"	30"	36"	Custom Len.	
$599.00	$604.31	$612.28	$620.24	$628.22	$636.19	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0232				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			23
12"	18"	24"	36"	48"	60"	Custom Len.	
$696.58	$711.91	$727.26	$757.94	$788.63	$819.32	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7867				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		24
12"	24"	36"	48"	60"	50CM	Custom Len.	
$50.89	$54.15	$57.87	$61.60	$65.32	$53.30	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C5895				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.			25
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.26	$72.40	$78.53	$84.67	$90.80	$70.19	See Web	
Part No. PE3C6208				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	26
12"	24"	36"	48"	60"	50CM	Custom Len.	
$57.61	$63.75	$69.88	$76.00	$82.14	$61.52	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C2884				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		27
12"	24"	36"	48"	60"	50CM	Custom Len.	
$343.44	$370.74	$398.04	$425.34	$452.64	$360.94	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34209				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	28
6"	12"	18"	24"	36"	48"	Custom Len.	
$167.07	$167.07	$171.09	$175.07	$183.06	$191.06	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34217				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	29
6"	12"	18"	24"	36"	48"	Custom Len.	
$174.44	$172.67	$181.02	$189.38	$206.07	$222.76	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE3417				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	30
6"	12"	18"	24"	36"	48"	Custom Len.	
$88.10	$92.41	$96.85	$101.29	$108.65	$112.99	See Web	
Part No. PE39424				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	31
6"	9"	12"	18"	24"	-	Custom Len.	
$67.43	$65.26	$67.43	$72.02	$76.62	-	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39438				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	32
6"	9"	12"	18"	24"	-	Custom Len.	
$33.61	$31.44	$33.61	$38.41	$43.20	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3646				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	33
6"	12"	18"	24"	36"	48"	Custom Len.	
$108.46	$112.81	$118.95	$120.06	$131.64	$143.24	See Web	
Part No. PE39416				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	34
6"	9"	12"	18"	24"	-	Custom Len.	
$67.29	$67.29	$71.31	$77.55	$83.79	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39430				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	35
6"	9"	12"	18"	24"	-	Custom Len.	
$35.72	$33.42	$35.72	$40.72	$45.70	-	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3655				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			36
6"	12"	18"	24"	36"	48"	Custom Len.	
$64.17	$64.60	$65.04	$61.74	$66.39	$63.30	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3514				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	37
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.66	$74.90	$73.81	$76.97	$88.26	$95.34	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3775				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	38
6"	12"	18"	24"	36"	48"	Custom Len.	
$70.79	$71.10	$71.41	$71.74	$69.33	$73.03	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3876				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	39
6"	12"	18"	24"	36"	48"	Custom Len.	
$95.12	$90.26	$96.27	$96.85	$92.37	$93.41	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3511				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	40
6"	12"	18"	24"	36"	48"	Custom Len.	
$77.34	$72.85	$80.04	$81.42	$84.15	$80.17	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE3347				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	41
6"	12"	18"	24"	36"	48"	Custom Len.	
$76.09	$80.66	$77.96	$79.82	$83.55	$87.29	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3428				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	42
6"	12"	18"	24"	36"	48"	Custom Len.	
$68.60	$70.26	$67.87	$69.46	$72.65	$80.73	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3515				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		43
6"	12"	18"	24"	36"	48"	Custom Len.	
$72.35	$74.03	$75.76	$77.45	$80.90	$84.54	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3987				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	44
6"	12"	18"	24"	36"	48"	Custom Len.	
$75.55	$77.22	$78.93	$80.65	$84.08	$82.43	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3713				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	45
6"	12"	18"	24"	36"	48"	Custom Len.	
$81.05	$81.05	$91.59	$88.72	$103.78	$104.05	See Web	

PE-P086EAM Coax, 50 Ohm

Part No. PE3CA1041				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.104" dia.			46
7"	12"	24"	36"	50CM	100CM	Custom Len.	
Call	$76.87	$90.33	$103.78	$85.41	$107.56	See Web	

PE-P141 Coax, 50 Ohm

Part No. PE3C1203				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.	11.2 dB/100ft	550 W	47
12"	24"	36"	48"	60"	50CM	Custom Len.	
$205.06	$217.85	$230.65	$243.45	$256.24	$213.25	See Web	

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1037				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			48
12"	20.500	24"	36"	50CM	100CM	Custom Len.	
$89.40	Call	$108.85	$129.56	$102.84	$135.35	See Web	

Standard Semi-Rigid Cable Assemblies

Continued on Next Page

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-020SR Coax, 50 Ohm

Part No. PE34211				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					85 dB/100ft	2.9 W	49
6"	12"	18"	24"	36"	48"	Custom Len.	
$167.84	$177.35	$186.90	$196.42	$215.48	$234.54	See Web	

PE-034SR Coax, 50 Ohm

Part No. PE34219				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					60 dB/100ft	10 W	50
6"	12"	18"	24"	36"	48"	Custom Len.	
$145.07	$151.69	$158.39	$165.03	$178.39	$191.73	See Web	

PE-047SR Coax, 50 Ohm

Part No. PE3147				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	51
6"	12"	18"	24"	36"	48"	Custom Len.	
$155.28	$160.68	$166.03	$171.42	$182.16	$192.95	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE3259				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					41 dB/100ft	32 W	52
6"	12"	18"	24"	36"	48"	Custom Len.	
$154.70	$159.45	$164.20	$168.96	$178.52	$188.07	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34208				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	53
6"	12"	18"	24"	36"	48"	Custom Len.	
$93.64	$99.26	$104.85	$108.90	$112.74	$122.95	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34213				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	54
6"	12"	18"	24"	36"	48"	Custom Len.	
$98.94	$103.57	$106.60	$111.17	$120.22	$129.32	See Web	

RG401/U Coax, 50 Ohm

Part No. PE34223				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	55
6"	12"	18"	24"	36"	48"	Custom Len.	
$179.97	$179.97	$191.88	$203.77	$227.56	$251.36	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3819				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	56
6"	12"	18"	24"	36"	48"	Custom Len.	
$92.55	$96.72	$95.27	$99.29	$112.34	$113.74	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3820				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	57
6"	12"	18"	24"	36"	48"	Custom Len.	
$98.03	$101.65	$105.27	$107.45	$114.68	$121.84	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34215				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	58
6"	12"	18"	24"	36"	48"	Custom Len.	
$175.71	$175.71	$185.55	$195.39	$215.06	$234.72	See Web	

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE3380				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	59
6"	12"	18"	24"	36"	48"	Custom Len.	
$88.38	$88.85	$89.37	$89.85	$90.82	$91.82	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE3858				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	60
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.78	$80.78	$82.07	$83.38	$85.98	$88.56	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE3444				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	61
6"	12"	18"	24"	36"	48"	Custom Len.	
$88.59	$89.32	$90.02	$90.77	$92.22	$93.67	See Web	

RG180B/U Coax, 95 Ohm

Part No. PE3141				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.		250 W	62
6"	12"	18"	24"	36"	48"	Custom Len.	
$70.96	$71.13	$73.34	$75.53	$79.91	$84.32	See Web	

SMA MALE RIGHT ANGLE TO SMA FEMALE

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C2305				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		63
12"	24"	36"	48"	60"	50CM	Custom Len.	
$244.91	$262.52	$280.13	$297.74	$315.33	$256.20	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7868				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		64
12"	24"	36"	48"	60"	50CM	Custom Len.	
$50.33	$54.09	$57.32	$61.05	$64.78	$52.74	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W02994				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	121.5 W	65
12"	24"	36"	48"	60"	50CM	Custom Len.	
$53.86	$63.21	$73.05	$82.89	$92.74	$59.67	See Web	

SMA MALE RIGHT ANGLE TO SMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-C100 Coax, 50 Ohm

Part No. PE3C7571				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24.5 dB/100ft	45 W	66
12"	24"	36"	48"	60"	50CM	Custom Len.	
$56.76	$58.32	$59.89	$61.45	$63.01	$57.76	See Web	

PE-C100-LSZH Coax, 50 Ohm

Part No. PE38574				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		67
12"	24"	36"	48"	60"	-	Custom Len.	
$57.05	$58.37	$59.70	$61.01	$62.34	-	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5244				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			68
12"	24"	36"	48"	60"	50CM	Custom Len.	
$281.42	$303.88	$326.33	$348.79	$371.24	$295.81	See Web	

Precision Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39428				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	69
6"	9"	12"	18"	24"	-	Custom Len.	
$47.64	$45.46	$47.64	$52.27	$56.38	-	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39442				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	70
6"	9"	12"	18"	24"	33"	Custom Len.	
$49.17	$46.95	Call	Call	$58.59	Call	See Web	

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7869				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		71
12"	24"	36"	48"	60"	50CM	Custom Len.	
$53.11	$56.35	$60.07	$63.80	$67.53	$55.01	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34307				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	72
6"	12"	18"	24"	36"	48"	Custom Len.	
$142.14	$145.97	$149.89	$153.72	$161.48	$169.21	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34319				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	73
6"	12"	18"	24"	36"	48"	Custom Len.	
$135.82	$143.97	$152.02	$160.17	$176.37	$192.56	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE34299				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	74
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.86	$78.87	$82.99	$87.14	$95.44	$103.72	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3C7582				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	75
12"	24"	36"	48"	60"	50CM	Custom Len.	
$60.16	$69.92	$79.69	$89.45	$99.21	$66.41	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE34313				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	76
6"	12"	18"	24"	36"	48"	Custom Len.	
$93.98	$93.98	$105.84	$105.75	$115.87	$127.46	See Web	

Part No. PE39420				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	77
6"	9"	12"	18"	24"	-	Custom Len.	
$56.01	$53.59	$56.01	$62.15	$68.28	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3156				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft		78
6"	12"	18"	24"	36"	48"	Custom Len.	
$60.21	$60.61	$61.06	$61.46	$62.27	$63.06	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3759				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	79
6"	12"	18"	24"	36"	48"	Custom Len.	
$66.61	$64.68	$67.84	$70.97	$77.28	$83.56	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3149				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	80
6"	12"	18"	24"	36"	48"	Custom Len.	
$72.09	$72.09	$78.18	$72.56	$79.13	$79.80	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3152				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	81
6"	12"	18"	24"	36"	48"	Custom Len.	
$73.26	$76.20	$76.78	$74.33	$78.52	$76.44	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3050				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	82
6"	12"	18"	24"	36"	48"	Custom Len.	
$74.08	$80.00	$75.30	$76.51	$85.49	$81.40	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE34179				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	83
6"	12"	18"	24"	36"	48"	Custom Len.	
$77.41	$74.81	$76.68	$78.55	$82.29	$86.04	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE34141				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	84
6"	12"	18"	24"	36"	48"	Custom Len.	
$75.08	$75.08	$75.85	$76.60	$78.11	$79.62	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3800				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	85
6"	12"	18"	24"	36"	48"	Custom Len.	
$64.80	$61.54	$63.14	$64.73	$67.93	$71.11	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3836				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	86
6"	12"	18"	24"	36"	48"	Custom Len.	
$73.69	$73.69	$75.28	$76.87	$80.04	$83.22	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34061				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	87
6"	12"	18"	24"	36"	48"	Custom Len.	
$75.69	$74.40	$76.00	$77.60	$80.81	$84.01	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE33749				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	88
6"	12"	18"	24"	36"	48"	Custom Len.	
$75.35	$75.35	$80.22	$85.09	$94.83	$104.56	See Web	

Standard Semi-Rigid Cable Assemblies

PE-020SR Coax, 50 Ohm

Part No. PE34309				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					85 dB/100ft	2.9 W	89
6"	12"	18"	24"	36"	48"	Custom Len.	
$167.20	$176.70	$186.20	$195.75	$214.82	$233.88	See Web	

PE-034SR Coax, 50 Ohm

Part No. PE34321				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					60 dB/100ft	10 W	90
6"	12"	18"	24"	36"	48"	Custom Len.	
$153.59	$160.23	$166.88	$173.56	$186.90	$200.19	See Web	

PE-047SR Coax, 50 Ohm

Part No. PE34303				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	91
6"	12"	18"	24"	36"	48"	Custom Len.	
$143.64	$149.04	$154.44	$159.77	$170.59	$181.30	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE34305				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	92
6"	12"	18"	24"	36"	48"	Custom Len.	
$143.05	$147.81	$152.56	$157.38	$166.88	$176.43	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34297				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	93
6"	12"	18"	24"	36"	48"	Custom Len.	
$69.98	$74.99	$80.01	$85.02	$95.04	$105.09	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34311				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	94
6"	12"	18"	24"	36"	48"	Custom Len.	
$91.68	$91.68	$96.42	$101.17	$109.15	$118.50	See Web	

RG401/U Coax, 50 Ohm

Part No. PE34315				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	95
6"	12"	18"	24"	36"	48"	Custom Len.	
$139.29	$150.85	$162.37	$173.90	$196.99	$220.09	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3679				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	96
6"	12"	18"	24"	36"	48"	Custom Len.	
$77.12	$77.12	$81.12	$85.15	$93.17	$101.21	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3925				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	97
6"	12"	18"	24"	36"	48"	Custom Len.	
$89.64	$89.64	$99.11	$97.19	$104.75	$110.73	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34317				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	98
6"	12"	18"	24"	36"	48"	Custom Len.	
$155.63	$155.63	$165.47	$175.31	$194.97	$214.63	See Web	

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE34160				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	99
6"	12"	18"	24"	36"	48"	Custom Len.	
$76.50	$76.99	$77.51	$77.96	$78.94	$79.95	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE34135				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	29.15 dB/100ft	240 W	1
6"	12"	18"	24"	36"	48"	Custom Len.	
$67.55	$68.85	$70.18	$71.43	$74.08	$76.71	See Web	

SMA MALE RIGHT ANGLE TO REVERSE POLARITY SMA MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W05106				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	2
12"	24"	36"	48"	60"	50CM	Custom Len.	
$95.71	$106.73	$107.35	$107.95	$108.56	$108.00	See Web	

SMA MALE RIGHT ANGLE TO REVERSE POLARITY SMA FEMALE

Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE3W03763				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft	600 W	3
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.28	$79.76	$86.25	$92.74	$99.24	$77.43	See Web	

SMA MALE RIGHT ANGLE TO SMB PLUG

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE33482				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	4
12"	24"	36"	48"	60"	-	Custom Len.	
$73.10	$73.74	$74.36	$75.03	$75.68	-	See Web	

SMA MALE RIGHT ANGLE TO SMB PLUG RIGHT ANGLE

Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE3W01739				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	5
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.76	$85.86	$97.97	$108.56	$120.50	$81.51	See Web	

SMA MALE RIGHT ANGLE TO SMC PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

Continued on Next Page

See Our Website For Current Pricing & Real-Time Stock Availability!

RG316/U Coax, 50 Ohm

Part No. PE3740				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	6
12"	24"	36"	48"	60"	50CM	Custom Len.	
$67.88	$66.19	$69.51	$72.86	$79.53	$64.99	See Web	

SMA MALE RIGHT ANGLE TO SSMC PLUG

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4424				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		7
6"	12"	18"	24"	36"	48"	Custom Len.	
$65.74	$66.18	$66.57	$66.99	$67.79	$68.61	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4446				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	8
6"	12"	18"	24"	36"	48"	Custom Len.	
$63.76	$67.90	$72.04	$76.17	$84.44	$92.72	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4407				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	9
6"	12"	18"	24"	36"	48"	Custom Len.	
$69.23	$70.71	$72.20	$73.66	$76.64	$79.59	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4438				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	10
6"	12"	18"	24"	36"	48"	Custom Len.	
$67.07	$68.53	$69.96	$71.40	$74.27	$77.14	See Web	

SMA MALE RIGHT ANGLE TO SSMC PLUG RIGHT ANGLE

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4425				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		11
6"	12"	18"	24"	36"	48"	Custom Len.	
$61.99	$66.15	$62.80	$63.21	$64.02	$64.83	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4485				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	12
6"	12"	18"	24"	36"	48"	Custom Len.	
$63.81	$68.36	$68.64	$72.76	$81.04	$89.32	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C4408				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	13
6"	12"	18"	24"	36"	48"	Custom Len.	
$68.37	$76.91	$71.47	$72.99	$76.09	$79.16	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4472				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	14
6"	12"	18"	24"	36"	48"	Custom Len.	
$66.46	$72.09	$69.58	$71.12	$74.22	$77.33	See Web	

SMA MALE RIGHT ANGLE TO SSMC JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4447				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	15
6"	12"	18"	24"	36"	48"	Custom Len.	
$61.89	$66.45	$64.53	$68.67	$76.94	$85.22	See Web	

SMA MALE RIGHT ANGLE TO TNC MALE

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C1179				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		16
6"	12"	24"	36"	48"	60"	Custom Len.	
Call	$242.53	$260.13	$277.74	$295.33	$312.93	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5261				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			17
12"	24"	36"	48"	60"	50CM	Custom Len.	
$262.97	$285.44	$307.90	$330.36	$352.80	$277.36	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0153				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			18
12"	18"	24"	36"	48"	60"	Custom Len.	
$506.82	$516.00	$525.19	$543.58	$561.96	$580.34	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0198				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			19
8"	12"	18"	24"	30"	36"	Custom Len.	
$498.30	$503.62	$511.58	$519.55	$527.51	$535.50	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0233				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			20
12"	18"	24"	36"	48"	60"	Custom Len.	
$570.61	$585.95	$601.29	$631.98	$662.66	$693.34	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE3C1617				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	5.5 dB/100ft		21
12"	24"	36"	48"	60"	50CM	Custom Len.	
$302.94	$330.25	$357.56	$384.85	$412.16	$320.45	See Web	

Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE3W06829				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			22
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.50	$74.97	$81.46	$87.94	$94.43	$72.63	See Web	

SMA MALE RIGHT ANGLE TO TNC MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C1409				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		23
12"	24"	36"	48"	60"	50CM	Custom Len.	
$349.76	$347.56	$365.16	$382.77	$401.79	$341.23	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5262				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			24
12"	24"	36"	48"	60"	50CM	Custom Len.	
$326.69	$349.15	$371.60	$394.05	$416.52	$341.08	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0155				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			25
12"	18"	24"	36"	48"	60"	Custom Len.	
$622.48	$631.67	$640.86	$659.24	$677.63	$696.01	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0200				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			26
8"	12"	18"	24"	30"	36"	Custom Len.	
$590.46	$595.79	$603.74	$611.72	$619.68	$627.66	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0234				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			27
12"	18"	24"	36"	48"	60"	Custom Len.	
$727.04	$742.37	$757.71	$788.40	$819.09	$849.77	See Web	

SMA MALE RIGHT ANGLE TO TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Semi-Rigid Cable Assemblies

PE-SR402AL Coax, 50 Ohm

Part No. PE3C2604				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	28
12"	24"	36"	48"	60"	50CM	Custom Len.	
$89.94	$100.96	$106.48	$115.88	$126.75	$91.48	See Web	

Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3C0056				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		29
12"	24"	36"	48"	60"	-	Custom Len.	
$58.63	$59.45	$55.93	$56.75	$57.58	-	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE3C1173				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		30
12"	24"	36"	48"	60"	50CM	Custom Len.	
$297.69	$298.44	$316.04	$333.65	$351.26	$292.12	See Web	

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-P160LL Coax, 50 Ohm

Part No. PE3C5263				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			31
12"	24"	36"	48"	60"	50CM	Custom Len.	
$291.47	$313.95	$336.40	$358.84	$381.31	$305.86	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0154				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			32
12"	18"	24"	36"	48"	60"	Custom Len.	
$592.32	$601.50	$610.69	$629.08	$647.46	$665.84	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0199				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			33
8"	12"	18"	24"	30"	36"	Custom Len.	
$586.19	$591.52	$599.47	$607.45	$615.42	$623.38	See Web	

Precision Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39484				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	34
6"	9"	12"	18"	24"	-	Custom Len.	
$51.85	$48.00	$51.85	$55.79	$60.20	-	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39498				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	35
6"	9"	12"	18"	24"	-	Custom Len.	
$55.78	$52.12	Call	Call	Call	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE39476				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	36
2.500//	6"	9"	12"	18"	24"	Custom Len.	
Call	$56.86	$58.59	$56.86	$63.23	Call	See Web	

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE3W00169				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.						450 W	37
12"	24"	36"	48"	60"	50CM	Custom Len.	
$89.45	$98.08	$106.70	$113.73	$124.60	$95.37	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39490				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	38
6"	9"	12"	18"	24"	-	Custom Len.	
$58.85	$49.41	$58.85	$63.61	$68.35	-	See Web	

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE33073				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		39
12"	24"	36"	48"	60"	-	Custom Len.	
$88.13	$91.56	$89.47	$98.63	$95.83	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE33759				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	40
12"	24"	36"	48"	60"	-	Custom Len.	
$86.71	$87.95	$95.62	$103.29	$109.40	-	See Web	

SMA MALE RIGHT ANGLE TO REVERSE POLARITY TNC MALE RIGHT ANGLE

Flexible Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE3C7914				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		41
12"	24"	36"	48"	60"	50CM	Custom Len.	
$85.59	$91.97	$98.34	$104.71	$109.54	$83.31	See Web	

SMA MALE RIGHT ANGLE TO NEX10 MALE

Low PIM Corrugated Cable Assemblies

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6259				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	42
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.18	$72.31	$78.45	$84.58	$90.71	$70.09	See Web	

REVERSE POLARITY SMA MALE RIGHT ANGLE TO N MALE

Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE35991				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	43
12"	24"	36"	48"	60"	-	Custom Len.	
$91.11	$106.54	$113.05	$121.55	$120.07	-	See Web	

REVERSE POLARITY SMA MALE RIGHT ANGLE TO N MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3W02390				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		44
12"	24"	36"	48"	60"	50CM	Custom Len.	
$81.40	$82.20	$82.99	$83.80	$84.60	$81.92	See Web	

REVERSE POLARITY SMA MALE RIGHT ANGLE TO SMA MALE

Standard Flexible Cable Assemblies

RG400/U Coax, 50 Ohm

Part No. PE3W06085				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	45
12"	24"	36"	48"	60"	50CM	Custom Len.	
$91.46	$99.84	$106.71	$114.96	$123.23	$88.46	See Web	

SMA FEMALE TO FAKRA PLUG

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE39344A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		46
12"	24"	36"	48"	60"	-	Custom Len.	
$45.75	$42.91	$44.25	$45.59	$46.94	-	See Web	
Part No. PE39344C				**Cable Dia.**	**Attn. @ 1 GHz**	**Power @ 1 GHz**	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		47
12"	24"	36"	48"	60"	-	Custom Len.	
$45.75	$42.91	$44.25	$45.59	$46.94	-	See Web	
Part No. PE39344D				**Cable Dia.**	**Attn. @ 1 GHz**	**Power @ 1 GHz**	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		48
12"	24"	36"	48"	60"	-	Custom Len.	
$45.75	$47.21	$44.25	$45.59	$46.94	-	See Web	
Part No. PE39344H				**Cable Dia.**	**Attn. @ 1 GHz**	**Power @ 1 GHz**	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		49
12"	24"	36"	48"	60"	-	Custom Len.	
$47.09	$44.16	$45.50	$46.82	$48.17	-	See Web	
Part No. PE39344I				**Cable Dia.**	**Attn. @ 1 GHz**	**Power @ 1 GHz**	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		50
12"	24"	36"	48"	60"	-	Custom Len.	
$45.75	$42.91	$44.25	$45.59	$46.94	-	See Web	
Part No. PE39344K				**Cable Dia.**	**Attn. @ 1 GHz**	**Power @ 1 GHz**	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		51
12"	24"	36"	48"	60"	-	Custom Len.	
$41.59	$47.21	$44.25	$45.59	$46.94	-	See Web	
Part No. PE39344Z				**Cable Dia.**	**Attn. @ 1 GHz**	**Power @ 1 GHz**	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		52
12"	24"	36"	48"	60"	-	Custom Len.	
$41.59	$46.38	$44.25	$45.59	$46.94	-	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE39345A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	53
12"	24"	36"	48"	60"	-	Custom Len.	
$49.32	$49.92	$50.45	$51.05	$51.65	-	See Web	
Part No. PE39345C				**Cable Dia.**	**Attn. @ 1 GHz**	**Power @ 1 GHz**	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	54
12"	24"	36"	48"	60"	-	Custom Len.	
$54.24	$49.92	$50.45	$51.05	$51.65	-	See Web	
Part No. PE39345D				**Cable Dia.**	**Attn. @ 1 GHz**	**Power @ 1 GHz**	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	55
12"	24"	36"	48"	60"	-	Custom Len.	
$49.32	$49.92	$50.45	$51.05	$51.65	-	See Web	
Part No. PE39345H				**Cable Dia.**	**Attn. @ 1 GHz**	**Power @ 1 GHz**	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	56
12"	24"	36"	48"	60"	-	Custom Len.	
$49.32	$49.92	$50.45	$51.05	$51.65	-	See Web	
Part No. PE39345I				**Cable Dia.**	**Attn. @ 1 GHz**	**Power @ 1 GHz**	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	57
12"	24"	36"	48"	60"	-	Custom Len.	
$49.32	$49.92	$50.45	$51.05	$51.65	-	See Web	
Part No. PE39345K				**Cable Dia.**	**Attn. @ 1 GHz**	**Power @ 1 GHz**	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	58
12"	24"	36"	48"	60"	-	Custom Len.	
$49.32	$49.92	$50.45	$51.05	$51.65	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

Part No. PE39345Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	59
12"	24"	36"	48"	60"	-	Custom Len.	
$54.24	$49.92	$50.45	$51.05	$51.65	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE39346A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	60
12"	24"	36"	48"	60"	-	Custom Len.	
$56.59	$59.75	$62.95	$66.12	$69.30	-	See Web	
Part No. PE39346C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	61
12"	24"	36"	48"	60"	-	Custom Len.	
$51.92	$54.60	$57.77	$60.94	$64.10	-	See Web	
Part No. PE39346D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	62
12"	24"	36"	48"	60"	-	Custom Len.	
$51.92	$54.60	$57.77	$60.94	$64.10	-	See Web	
Part No. PE39346H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	63
12"	24"	36"	48"	60"	-	Custom Len.	
$51.92	$54.60	$57.77	$60.94	$64.10	-	See Web	
Part No. PE39346I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	64
12"	24"	36"	48"	60"	-	Custom Len.	
$56.59	$59.75	$62.95	$66.12	$69.30	-	See Web	
Part No. PE39346K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	65
12"	24"	36"	48"	60"	-	Custom Len.	
$56.58	$54.60	$57.77	$60.94	$64.10	-	See Web	
Part No. PE39346Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	66
12"	24"	36"	48"	60"	-	Custom Len.	
$51.92	$54.60	$57.77	$60.94	$64.10	-	See Web	

SMA FEMALE TO FAKRA JACK

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE39349A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		67
12"	24"	36"	48"	60"	-	Custom Len.	
$45.75	$42.91	$44.25	$45.59	$46.94	-	See Web	
Part No. PE39349B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		68
12"	24"	36"	48"	60"	-	Custom Len.	
$45.75	$42.91	$44.25	$45.59	$46.94	-	See Web	
Part No. PE39349C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		69
12"	24"	36"	48"	60"	-	Custom Len.	
$45.75	$42.91	$44.25	$45.59	$51.74	-	See Web	
Part No. PE39349D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		70
12"	24"	36"	48"	60"	-	Custom Len.	
$43.27	$44.74	$43.51	$44.84	$49.27	-	See Web	
Part No. PE39349H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		71
12"	24"	36"	48"	60"	-	Custom Len.	
$45.75	$42.91	$44.25	$45.59	$46.94	-	See Web	
Part No. PE39349I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		72
12"	24"	36"	48"	60"	-	Custom Len.	
$45.75	$42.91	$44.25	$45.59	$46.94	-	See Web	
Part No. PE39349K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		73
12"	24"	36"	48"	60"	-	Custom Len.	
$41.59	$47.21	$44.25	$45.59	$46.94	-	See Web	
Part No. PE39349Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft		74
12"	24"	36"	48"	60"	-	Custom Len.	
$45.75	$42.91	$48.68	$45.59	$51.74	-	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE39350A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	75
12"	24"	36"	48"	60"	-	Custom Len.	
$54.24	$54.23	$54.71	$55.18	$55.68	-	See Web	
Part No. PE39350B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	76
12"	24"	36"	48"	60"	-	Custom Len.	
$53.27	$53.75	$54.22	$54.21	$54.69	-	See Web	
Part No. PE39350C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	77
12"	24"	36"	48"	60"	-	Custom Len.	
$54.24	$54.23	$54.71	$55.18	$55.68	-	See Web	
Part No. PE39350D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	78
12"	24"	36"	48"	60"	-	Custom Len.	
$52.28	$49.92	$50.45	$51.05	$51.65	-	See Web	
Part No. PE39350H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	79
12"	24"	36"	48"	60"	-	Custom Len.	
$49.32	$49.92	$50.45	$51.05	$51.65	-	See Web	
Part No. PE39350I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	80
12"	24"	36"	48"	60"	-	Custom Len.	
$49.32	$49.92	$50.45	$51.05	$51.65	-	See Web	
Part No. PE39350K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	81
12"	24"	36"	48"	60"	-	Custom Len.	
$54.24	$54.23	$54.71	$55.18	$55.68	-	See Web	
Part No. PE39350Z				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	82
12"	24"	36"	48"	60"	-	Custom Len.	
$59.13	$54.23	$54.71	$55.18	$55.68	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE39351A				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	83
12"	24"	36"	48"	60"	-	Custom Len.	
$56.59	$59.75	$62.95	$66.12	$69.30	-	See Web	
Part No. PE39351B				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	84
12"	24"	36"	48"	60"	-	Custom Len.	
$51.92	$54.60	$57.77	$60.94	$64.10	-	See Web	
Part No. PE39351C				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	85
12"	24"	36"	48"	60"	-	Custom Len.	
$62.23	$59.75	$62.95	$66.12	$69.30	-	See Web	
Part No. PE39351D				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	86
12"	24"	36"	48"	60"	-	Custom Len.	
$56.59	$59.75	$62.95	$66.12	$69.30	-	See Web	
Part No. PE39351H				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	87
12"	24"	36"	48"	60"	-	Custom Len.	
$51.92	$54.60	$57.77	$60.94	$64.10	-	See Web	
Part No. PE39351I				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	88
12"	24"	36"	48"	60"	-	Custom Len.	
$51.92	$54.60	$57.77	$60.94	$64.10	-	See Web	
Part No. PE39351K				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	89
12"	24"	36"	48"	60"	-	Custom Len.	
$51.92	$54.60	$57.77	$60.94	$64.10	-	See Web	

SMA FEMALE TO MCX PLUG RIGHT ANGLE

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W03859				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	90
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.14	$83.99	$93.82	$103.67	$111.95	$80.44	See Web	

SMA FEMALE TO MMCX PLUG

Standard Flexible Cable Assemblies

RG188-DS Coax, 50 Ohm

Part No. PE3W03032				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.118" dia.	30 dB/100ft	160 W	91
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.26	$69.33	$73.40	$77.45	$81.52	$67.87	See Web	

SMA FEMALE TO N MALE

Low Loss Flexible Cable Assemblies

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0141				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			92
12"	18"	24"	36"	48"	60"	Custom Len.	
$461.57	$470.76	$479.95	$498.33	$516.71	$535.10	See Web	

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

Precision Flexible Cable Assemblies

PE-P141 Coax, 50 Ohm

Part No. PE356				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			93
12"	24"	36"	48"	60"	72"	Custom Len.	
$188.89	$189.82	$213.52	$226.54	$224.62	$251.63	See Web	

SMA FEMALE TO N MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0143				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			94
12"	18"	24"	36"	48"	60"	Custom Len.	
$586.28	$595.47	$604.65	$623.04	$641.42	$659.80	See Web	

SMA FEMALE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C3159				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		95
12"	24"	36"	48"	60"	50CM	Custom Len.	
$212.90	$229.98	$247.08	$264.17	$281.25	$223.85	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0142				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			96
12"	18"	24"	36"	48"	60"	Custom Len.	
$556.09	$565.29	$574.48	$592.87	$611.24	$629.63	See Web	

SMA FEMALE TO QMA MALE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38278				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	97
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.37	$54.66	$55.39	$56.19	$56.91	$57.64	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE38277				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	98
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.55	$66.27	$62.19	$62.99	$63.78	$64.56	See Web	

RG316/U Coax, 50 Ohm

Part No. PE38276				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	99
12"	24"	36"	48"	60"	72"	Custom Len.	
$75.44	$78.88	$76.19	$79.37	$82.56	$85.72	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE38052				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	26.1 dB/100ft	160 W	1
12"	24"	36"	48"	60"	72"	Custom Len.	
$84.96	$88.20	$91.43	$94.65	$97.83	$101.05	See Web	

SMA FEMALE TO SMA MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0137				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			2
12"	18"	24"	36"	48"	60"	Custom Len.	
$558.11	$567.30	$576.50	$594.88	$613.26	$631.65	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W03981				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	3
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.01	$54.13	$54.75	$55.37	$55.98	$54.41	See Web	

SMA FEMALE TO SMA FEMALE

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C0045				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		4
12"	24"	36"	48"	60"	-	Custom Len.	
$63.41	$59.55	$60.37	$61.21	$66.81	-	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE3C1239				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		5
12"	24"	36"	48"	60"	50CM	Custom Len.	
$198.40	$216.01	$233.61	$251.22	$268.82	$209.69	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0135				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			6
12"	18"	24"	36"	48"	60"	Custom Len.	
$521.91	$531.10	$540.30	$558.67	$577.06	$595.45	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34833				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	7
6"	12"	18"	24"	36"	48"	Custom Len.	
$120.38	$115.43	$119.42	$133.46	$131.42	$139.40	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE3534				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	8
6"	12"	18"	24"	36"	48"	Custom Len.	
$98.10	$106.27	$112.94	$120.99	$137.19	$153.40	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE33964				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	9
6"	12"	18"	24"	36"	48"	Custom Len.	
$68.23	$68.23	$72.38	$76.51	$84.80	$93.10	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE34292				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	10
6"	12"	18"	24"	36"	48"	Custom Len.	
$96.35	$96.35	$102.73	$107.58	$120.16	$132.73	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE33547				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	11
12"	24"	36"	48"	60"	-	Custom Len.	
$69.41	$65.07	$65.88	$72.14	$67.50	-	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3578				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	12
12"	24"	36"	48"	60"	-	Custom Len.	
$52.71	$58.52	$64.83	$76.84	$77.42	-	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE33120				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	13
12"	24"	36"	48"	60"	-	Custom Len.	
$63.63	$69.35	$64.57	$70.66	$65.55	-	See Web	

RG223/U Coax, 50 Ohm

Part No. PE33254				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	14
12"	24"	36"	48"	60"	-	Custom Len.	
$47.11	$50.05	$52.98	$59.97	$58.35	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE33047				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		15
12"	24"	36"	48"	60"	-	Custom Len.	
$70.33	$73.77	$72.69	$80.84	$84.35	-	See Web	

Standard Semi-Rigid Cable Assemblies

PE-020SR Coax, 50 Ohm

Part No. PE34917				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					85 dB/100ft	2.9 W	16
6"	12"	18"	24"	36"	48"	Custom Len.	
$185.65	$196.77	$195.46	$205.29	$224.96	$244.65	See Web	

PE-034SR Coax, 50 Ohm

Part No. PE34405				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					60 dB/100ft	10 W	17
6"	12"	18"	24"	36"	48"	Custom Len.	
$163.99	$170.46	$167.48	$174.14	$187.46	$200.78	See Web	

PE-047SR Coax, 50 Ohm

Part No. PE3758				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	18
6"	12"	18"	24"	36"	48"	Custom Len.	
$115.30	$121.13	$122.01	$133.13	$145.11	$149.75	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE34835				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	19
6"	12"	18"	24"	36"	48"	Custom Len.	
$121.33	$115.17	$120.08	$125.00	$134.84	$144.69	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-SR402AL Coax, 50 Ohm

Part No. PE34836				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	20
6"	12"	18"	24"	36"	48"	Custom Len.	
$70.35	$74.57	$75.52	$80.68	$91.05	$101.37	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34834				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	21
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.28	$89.99	$89.52	$94.05	$103.31	$110.91	See Web	

RG401/U Coax, 50 Ohm

Part No. PE3521				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	22
6"	12"	18"	24"	36"	48"	Custom Len.	
$118.40	$118.40	$130.31	$142.19	$165.99	$189.80	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3931				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	23
6"	12"	18"	24"	36"	48"	Custom Len.	
$67.86	$72.03	$76.33	$75.98	$84.02	$92.04	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3109				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	24
6"	12"	18"	24"	36"	48"	Custom Len.	
$68.95	$68.95	$72.74	$76.51	$84.06	$91.62	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE3524				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	25
6"	12"	18"	24"	36"	48"	Custom Len.	
$99.53	$107.67	$117.22	$126.73	$145.79	$164.86	See Web	

Standard Flexible Cable Assemblies

RG62A/U Coax, 93 Ohm

Part No. PE3424				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	26
12"	24"	36"	48"	60"	-	Custom Len.	
$69.98	$71.36	$72.74	$74.14	$75.53	-	See Web	

SMA FEMALE TO SMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0136				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			27
12"	18"	24"	36"	48"	60"	Custom Len.	
$557.31	$566.50	$575.69	$594.08	$612.45	$630.85	See Web	

SMA FEMALE TO SSMC PLUG

Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W06055				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		28
12"	24"	36"	48"	60"	50CM	Custom Len.	
$49.39	$50.19	$50.98	$51.80	$52.61	$49.89	See Web	

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4426				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		29
6"	12"	18"	24"	36"	48"	Custom Len.	
$59.67	$66.09	$66.50	$60.90	$61.72	$62.52	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4393				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	30
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.27	$88.87	$81.31	$81.80	$82.84	$83.86	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4409				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	31
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.31	$72.87	$74.41	$75.93	$79.03	$82.10	See Web	

SMA FEMALE TO SSMC PLUG RIGHT ANGLE

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4427				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		32
6"	12"	18"	24"	36"	48"	Custom Len.	
$55.91	$59.70	$60.11	$57.13	$57.94	$58.76	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4464				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	33
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.01	$71.54	$72.05	$72.56	$73.59	$74.62	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4410				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	34
6"	12"	18"	24"	36"	48"	Custom Len.	
$67.55	$69.09	$70.64	$72.16	$75.26	$78.33	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4473				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	35
6"	12"	18"	24"	36"	48"	Custom Len.	
$66.45	$68.00	$69.56	$71.11	$74.21	$77.32	See Web	

SMA FEMALE TO SSMC JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4394				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	36
6"	12"	18"	24"	36"	48"	Custom Len.	
$75.90	$84.06	$76.93	$77.44	$78.47	$79.49	See Web	

SMA FEMALE TO TNC MALE

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W00825				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		37
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.10	$58.91	$59.72	$60.54	$61.34	$58.62	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3W00245				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.			38
12"	24"	36"	48"	60"	50CM	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE3C3205				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		39
12"	24"	36"	48"	60"	50CM	Custom Len.	
$187.38	$204.99	$222.58	$240.18	$257.78	$198.65	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0138				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			40
12"	18"	24"	36"	48"	60"	Custom Len.	
$470.61	$479.80	$488.99	$507.38	$525.75	$544.15	See Web	

SMA FEMALE TO TNC MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0140				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			41
12"	18"	24"	36"	48"	60"	Custom Len.	
$586.28	$595.47	$604.65	$623.04	$641.42	$659.80	See Web	

SMA FEMALE TO TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0139				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			42
12"	18"	24"	36"	48"	60"	Custom Len.	
$556.09	$565.29	$574.48	$592.87	$611.24	$629.63	See Web	

SMA FEMALE RIGHT ANGLE TO SMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Precision Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39434				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	121.5 W	43
6"	9"	12"	18"	24"	-	Custom Len.	
$58.11	$60.09	$60.09	$67.01	$68.28	-	See Web	

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

See Our Website For Current Pricing & Real-Time Stock Availability!

SMA FEMALE BULKHEAD TO SMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

M17/113-RG316-27478 Coax, 50 Ohm

Part No. PE3M0095				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.			44
6"	8"	12"	16"	18"	24"	Custom Len.	
$202.11	$202.46	$203.19	$203.91	$204.28	$205.36	See Web	

M17/119-RG174-0XDS2 Coax, 50 Ohm

Part No. PE3M0110				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.			45
6"	8"	12"	16"	18"	24"	Custom Len.	
$201.44	$201.58	$222.05	$202.14	$202.27	$202.71	See Web	

SMA FEMALE BULKHEAD TO TNC MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

M17/113-RG316-27478 Coax, 50 Ohm

Part No. PE3M0098				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.			46
6"	8"	12"	16"	18"	24"	Custom Len.	
$203.15	$203.51	$204.24	$204.96	$205.33	$206.41	See Web	

M17/119-RG174-0XDS2 Coax, 50 Ohm

Part No. PE3M0113				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.			47
6"	8"	12"	16"	18"	24"	Custom Len.	
$202.49	$202.61	$202.90	$203.18	$203.33	$203.75	See Web	

SMA FEMALE BULKHEAD TO MCX PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Precision Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39421				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	48
6"	9"	12"	18"	24"	-	Custom Len.	
$48.12	$43.72	$48.12	$54.04	$60.41	-	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39435				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	49
6"	9"	12"	18"	24"	-	Custom Len.	
$42.31	$40.00	$42.31	$47.29	$52.27	-	See Web	

SMA FEMALE BULKHEAD TO MMCX PLUG

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE35575				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	50
12"	24"	36"	48"	60"	-	Custom Len.	
$63.94	$67.39	$70.81	$69.86	$73.02	-	See Web	

SMA FEMALE BULKHEAD TO MMCX PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Precision Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39422				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	51
6"	9"	12"	18"	24"	-	Custom Len.	
$47.87	$44.80	$47.87	$54.31	$60.17	-	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39436				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	121.5 W	52
6"	9"	12"	18"	24"	-	Custom Len.	
$64.36	$62.07	$64.36	$69.30	$74.22	-	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE34786				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	53
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.96	$64.57	$65.17	$65.80	$66.40	$64.37	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3C3821				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	54
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.37	$67.84	$68.95	$70.09	$71.22	$67.42	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE3W00934				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	55
12"	50CM	24"	36"	100CM	48"	Custom Len.	
$75.95	$78.37	$79.71	$83.47	$84.53	$87.23	See Web	

RG316/U Coax, 50 Ohm

Part No. PE34686				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	56
12"	24"	36"	48"	60"	-	Custom Len.	
$64.93	$68.35	$71.79	$71.94	$78.93	-	See Web	

Part No. PE3C1081				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	57
12"	50CM	24"	36"	100CM	48"	Custom Len.	
$64.58	$63.07	$64.26	$67.60	$68.54	$70.94	See Web	

SMA FEMALE BULKHEAD TO N MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0149				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			58
12"	18"	24"	36"	48"	60"	Custom Len.	
$496.97	$506.15	$515.34	$533.73	$552.10	$570.49	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0194				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			59
8"	12"	18"	24"	30"	36"	Custom Len.	
$479.88	$485.20	$493.16	$501.13	$509.12	$517.07	See Web	

SMA FEMALE BULKHEAD TO N MALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0151				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			60
12"	18"	24"	36"	48"	60"	Custom Len.	
$621.68	$630.87	$640.06	$658.45	$676.82	$695.22	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0196				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			61
8"	12"	18"	24"	30"	36"	Custom Len.	
$586.19	$591.52	$599.47	$607.45	$615.42	$623.38	See Web	

SMA FEMALE BULKHEAD TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0150				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			62
12"	18"	24"	36"	48"	60"	Custom Len.	
$591.51	$600.70	$609.88	$628.27	$646.65	$665.03	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0195				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			63
8"	12"	18"	24"	30"	36"	Custom Len.	
$590.46	$595.79	$603.74	$611.72	$619.68	$627.66	See Web	

SMA FEMALE BULKHEAD TO SMA MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE3468				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	64
6"	12"	18"	24"	36"	48"	Custom Len.	
$65.15	$69.46	$73.90	$73.81	$82.11	$90.39	See Web	

Part No. PE39427				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	400 W	65
6"	9"	12"	18"	24"	-	Custom Len.	
$57.67	$55.50	$57.67	$62.26	Call	-	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3W04417				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	66
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.44	$63.70	$73.48	$83.24	$93.00	$60.18	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

Standard Flexible Cable Assemblies

RG316-DS Coax, 50 Ohm

Part No. PE3973				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	67
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$58.67	$60.33	$62.05	$63.78	$63.31	$66.51	See Web	

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1038				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	68
1 piece price shown. See web or call for volume pricing.				0.163" dia.			
12"	24"	36"	50CM	100CM	-	Custom Len.	
$87.60	$110.16	$133.95	Call	$125.56	-	See Web	

SMA FEMALE BULKHEAD TO SMA MALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3W05962				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	69
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$36.66	$37.37	$38.09	$38.80	$39.53	$37.12	See Web	

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE3W07670				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	70
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.7 dB/100ft	135 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$44.51	$45.41	$45.87	$46.78	$47.69	$44.63	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0145					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	71
1 piece price shown. See web or call for volume pricing.					0.195" dia.			
12"	18"	24"	36"	48"	60"	Custom Len.		
$593.52	$602.71	$611.89	$630.28	$648.66	$667.05	See Web		

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0190					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	72
1 piece price shown. See web or call for volume pricing.					0.16" dia.			
8"	12"	18"	24"	30"	36"	Custom Len.		
$594.73	$600.04	$608.01	$615.98	$623.95	$631.92	See Web		

SMA FEMALE BULKHEAD TO SMA FEMALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W07334				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	73
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$54.21	$57.81	$61.42	$65.03	$68.64	$56.52	See Web	

SMA FEMALE BULKHEAD TO SMA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5247				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	74
1 piece price shown. See web or call for volume pricing.				0.16" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$259.63	$308.73	$299.98	$322.08	$344.21	$269.90	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0144					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	75
1 piece price shown. See web or call for volume pricing.					0.195" dia.			
12"	18"	24"	36"	48"	60"	Custom Len.		
$592.71	$601.90	$611.09	$629.47	$647.86	$666.25	See Web		

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0189					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	76
1 piece price shown. See web or call for volume pricing.					0.16" dia.			
8"	12"	18"	24"	30"	36"	Custom Len.		
$590.46	$595.79	$603.74	$611.72	$619.68	$627.66	See Web		

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34709				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	77
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$130.49	$134.40	$138.23	$142.14	$149.89	$157.61	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE3794				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	78
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$116.91	$132.54	$133.10	$141.23	$157.44	$173.64	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE33864				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	79
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$78.75	$78.75	$83.35	$87.93	$97.12	$106.31	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE34070				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	80
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$84.49	$84.49	$95.80	$96.25	$106.52	$118.11	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE35404				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	81
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$61.90	$62.71	$63.51	$70.82	$65.12	-	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE33382				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	82
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$58.18	$58.77	$59.30	$59.88	$60.41	-	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE33084				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	83
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$77.94	$79.01	$84.95	$86.18	$82.15	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE33158				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	84
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		
12"	24"	36"	48"	60"	-	Custom Len.	
$64.39	$71.70	$70.72	$73.90	$77.08	-	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE38184				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	85
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$70.97	$78.66	$77.37	$85.75	$89.25	-	See Web	

Standard Semi-Rigid Cable Assemblies

PE-020SR Coax, 50 Ohm

Part No. PE3932				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	86
1 piece price shown. See web or call for volume pricing.					85 dB/100ft	2.9 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$166.48	$176.03	$185.54	$195.09	$214.16	$233.23	See Web	

PE-034SR Coax, 50 Ohm

Part No. PE3520				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	87
1 piece price shown. See web or call for volume pricing.					60 dB/100ft	10 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$162.06	$168.74	$175.39	$182.09	$195.37	$208.71	See Web	

PE-047SR Coax, 50 Ohm

Part No. PE33789				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	88
1 piece price shown. See web or call for volume pricing.				0.047" dia.	40 dB/100ft	32 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$145.64	$145.64	$151.18	$156.74	$167.84	$178.94	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE3929				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	89
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$131.42	$136.17	$140.98	$145.71	$155.22	$164.78	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE3903				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	90
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$63.25	$68.25	$73.28	$78.29	$88.33	$98.37	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34071				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	91
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.54	$80.54	$85.29	$90.04	$99.55	$107.53	See Web	

RG401/U Coax, 50 Ohm

Part No. PE3634				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	92
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$120.34	$131.85	$143.45	$154.95	$178.05	$201.14	See Web	

RG402/U Coax, 50 Ohm

Part No. PE33518				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	93
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$71.30	$71.30	$75.31	$79.33	$87.37	$95.40	See Web	

RG405/U Coax, 50 Ohm

Part No. PE33176				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	94
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.08	$84.88	$83.85	$87.63	$95.17	$102.73	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE3764				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	95
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$118.34	$127.89	$137.40	$146.95	$166.03	$185.09	See Web	

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

See Our Website For Current Pricing & Real-Time Stock Availability!

SMA FEMALE BULKHEAD TO REVERSE POLARITY SMA MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG141A/U Coax, 50 Ohm

Part No. PE3W02965				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$77.03	$85.14	$93.24	$101.35	$107.95	$82.23	See Web

96

SMA FEMALE BULKHEAD TO SMB PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-C100-LSZH Coax, 50 Ohm

Part No. PE3W00135				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.109" dia.	25 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$47.20	$48.62	$50.06	$51.49	$52.91	$48.13	See Web

97

SMA FEMALE BULKHEAD TO SMP FEMALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

PE-P086 Coax, 50 Ohm

Part No. PE3C5233				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.104" dia.	21.7 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$67.98	$76.46	$84.94	$93.40	$101.88	$73.41	See Web

98

SMA FEMALE BULKHEAD TO SMP FEMALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C3937				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$55.16	$54.36	$54.67	$55.47	$56.29	$54.07	See Web

99

SMA FEMALE BULKHEAD TO SSMC PLUG

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4428				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
6"	12"	18"	24"	36"	48"	Custom Len.
$54.30	$59.21	$56.26	$58.92	$57.47	$65.09	See Web

1

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4448				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	18"	24"	36"	48"	Custom Len.
$64.53	$75.56	$72.83	$76.95	$85.23	$93.50	See Web

2

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4395				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
6"	12"	18"	24"	36"	48"	Custom Len.
$81.61	$82.18	$75.23	$75.73	$76.75	$77.79	See Web

3

RG316/U Coax, 50 Ohm

Part No. PE3C4411				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
6"	12"	18"	24"	36"	48"	Custom Len.
$67.07	$72.74	$70.17	$71.70	$79.62	$83.25	See Web

4

SMA FEMALE BULKHEAD TO SSMC PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4429				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
6"	12"	18"	24"	36"	48"	Custom Len.
$51.00	$52.56	$52.97	$55.15	$54.19	$61.32	See Web

5

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4486				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	18"	24"	36"	48"	Custom Len.
$61.14	$71.81	$69.42	$81.19	$81.81	$90.10	See Web

6

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4465				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
6"	12"	18"	24"	36"	48"	Custom Len.
$64.95	$69.38	$65.96	$66.48	$67.50	$68.53	See Web

7

RG316/U Coax, 50 Ohm

Part No. PE3C4412				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
6"	12"	18"	24"	36"	48"	Custom Len.
$63.30	$68.75	$70.46	$67.93	$71.01	$74.09	See Web

8

RG316-DS Coax, 50 Ohm

Part No. PE3C4474				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W
6"	12"	18"	24"	36"	48"	Custom Len.
$69.63	$78.32	$80.04	$74.31	$77.41	$80.52	See Web

9

SMA FEMALE BULKHEAD TO SSMC JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4449				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	18"	24"	36"	48"	Custom Len.
$57.05	$61.19	$65.32	$69.46	$77.73	$86.01	See Web

10

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4396				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
6"	12"	18"	24"	36"	48"	Custom Len.
$69.82	$70.35	$70.84	$71.36	$72.39	$73.41	See Web

11

SMA FEMALE BULKHEAD TO TNC MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5264				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$241.18	$263.65	$286.09	$308.56	$331.01	$255.57	See Web

12

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0146				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.		
12"	18"	24"	36"	48"	60"	Custom Len.
$506.02	$515.21	$524.40	$542.78	$561.16	$579.55	See Web

13

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0191				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
8"	12"	18"	24"	30"	36"	Custom Len.
$494.03	$499.35	$507.32	$515.28	$523.26	$531.22	See Web

14

SMA FEMALE BULKHEAD TO TNC MALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5265				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
12"	24"	36"	48"	60"	50CM	Custom Len.
$304.90	$263.65	$286.09	$308.56	$331.01	$255.57	See Web

15

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0148				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.		
12"	18"	24"	36"	48"	60"	Custom Len.
$621.68	$630.87	$640.06	$658.45	$676.82	$695.22	See Web

16

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0193				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
8"	12"	18"	24"	30"	36"	Custom Len.
$586.19	$591.52	$599.47	$607.45	$615.42	$623.38	See Web

17

See Our Website For Current Pricing & Real-Time Stock Availability!

SMA FEMALE BULKHEAD TO TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5266				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			18
12"	24"	36"	48"	60"	50CM	Custom Len.	
$269.68	$292.15	$314.60	$337.05	$359.51	$284.06	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0147				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			19
12"	18"	24"	36"	48"	60"	Custom Len.	
$591.76	$600.70	$609.88	$628.27	$646.65	$665.03	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0192				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			20
8"	12"	18"	24"	30"	36"	Custom Len.	
$581.93	$587.24	$595.22	$603.18	$611.16	$619.11	See Web	

SMA FEMALE BULKHEAD TO HMCX32 1.2 PLUG

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1007				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			21
3"	6"	12"	-	-	-	Custom Len.	
$15.89	$14.76	$20.10	-	-	-	See Web	

SMA FEMALE BULKHEAD TO UMCX PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38299				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	22
3"	6"	9"	12"	18"	24"	Custom Len.	
$73.40	$75.28	$77.16	$79.05	$82.93	$84.09	See Web	

SMA FEMALE BULKHEAD TO UMCX 2.1 PLUG

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1005				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			23
3"	6"	12"	-	-	-	Custom Len.	
$12.80	$14.76	$14.07	-	-	-	See Web	

SMA FEMALE BULKHEAD TO UMCX 2.5 PLUG

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3CA1003				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.07" dia.			24
3"	6"	9"	12"	14"	15"	Custom Len.	
Call	$14.76	$14.76	$13.71	Call	Call	See Web	

RG178-DS Coax, 50 Ohm

Part No. PE3CA1004				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.086" dia.			25
3"	6"	9"	12"	-	-	Custom Len.	
Call	$15.32	$15.52	$19.00	-	-	See Web	

PE-81mm Coax, 50 Ohm

Part No. PE3CA1000				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			26
3"	6"	12"	-	-	-	Custom Len.	
$14.76	$13.05	$14.76	-	-	-	See Web	

PE-113mm Coax, 50 Ohm

Part No. PE3CA1001				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.044" dia.			27
3"	6"	9"	12"	-	-	Custom Len.	
$16.29	$14.13	$14.33	$14.13	-	-	See Web	

PE-137mm Coax, 50 Ohm

Part No. PE3CA1002				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.053" dia.			28
3"	6"	12"	-	-	-	Custom Len.	
$14.76	$15.42	$14.76	-	-	-	See Web	

SMA FEMALE BULKHEAD TO WMCX 1.6 PLUG

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1006				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			29
3"	10CM	6"	12"	-	-	Custom Len.	
$12.80	Call	$14.76	$14.76	-	-	See Web	

REVERSE POLARITY SMA FEMALE BULKHEAD TO SMA MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W04623				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	30
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.12	$84.97	$94.82	$104.66	$112.92	$81.44	See Web	

REVERSE POLARITY SMA FEMALE BULKHEAD TO SMA MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W04625				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	31
12"	24"	36"	48"	60"	50CM	Custom Len.	
$97.86	$107.70	$115.91	$125.62	$135.33	$104.17	See Web	

REVERSE POLARITY SMA FEMALE BULKHEAD TO HMCX32 1.2 PLUG

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1022				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			32
3"	6"	12"	-	-	-	Custom Len.	
$14.76	$14.76	$16.41	-	-	-	See Web	

REVERSE POLARITY SMA FEMALE BULKHEAD TO UMCX PLUG

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38300				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	33
3"	6"	9"	12"	18"	24"	Custom Len.	
$60.61	$60.61	$60.61	$60.61	$64.66	$72.01	See Web	

REVERSE POLARITY SMA FEMALE BULKHEAD TO UMCX 2.1 PLUG

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1033				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			34
3"	6"	9"	12"	-	-	Custom Len.	
$14.76	$16.29	Call	$14.76	-	-	See Web	

REVERSE POLARITY SMA FEMALE BULKHEAD TO UMCX 2.5 PLUG

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3CA1019				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.07" dia.			35
3"	6"	9"	12"	-	-	Custom Len.	
Call	$12.80	$14.07	$14.76	-	-	See Web	

RG178-DS Coax, 50 Ohm

Part No. PE3CA1020				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.086" dia.			36
3"	6"	9"	12"	-	-	Custom Len.	
Call	$16.03	$16.03	$13.71	-	-	See Web	

PE-81mm Coax, 50 Ohm

Part No. PE3CA1016				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			37
3"	6"	12"	-	-	-	Custom Len.	
$12.80	$14.76	$13.71	-	-	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

PE-113mm Coax, 50 Ohm

Part No. PE3CA1017				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	38
1 piece price shown. See web or call for volume pricing.				0.044" dia.			
3"	6"	12"	-	-	-	Custom Len.	
$14.76	$14.76	$14.76	-	-	-	See Web	

PE-137mm Coax, 50 Ohm

Part No. PE3CA1018				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	39
1 piece price shown. See web or call for volume pricing.				0.053" dia.			
3"	6"	12"	-	-	-	Custom Len.	
$14.76	$14.76	$14.76	-	-	-	See Web	

REVERSE POLARITY SMA FEMALE BULKHEAD TO WMCX 1.6 PLUG

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1021				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	40
1 piece price shown. See web or call for volume pricing.				0.032" dia.			
3"	6"	12"	-	-	-	Custom Len.	
$12.80	$12.80	$14.76	-	-	-	See Web	

REVERSE THREAD SMA FEMALE BULKHEAD TO UMCX PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38301				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	41
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	
3"	6"	9"	12"	18"	24"	Custom Len.	
$64.44	$65.29	$66.27	$67.13	$68.00	$68.85	See Web	

SMA FEMALE 2 HOLE FLANGE TO SMA FEMALE 2 HOLE FLANGE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE35154				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	42
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$95.78	$105.36	$99.84	$103.90	$110.45	$118.42	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE35108				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	43
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$84.49	$88.45	$92.49	$96.49	$104.56	$110.98	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE35114				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	44
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$74.86	$80.53	$86.21	$91.95	$108.78	$113.12	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE35064				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	45
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$99.05	$104.95	$104.65	$115.49	$119.83	$130.94	See Web	

RG402/U Coax, 50 Ohm

Part No. PE3525				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	46
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$84.36	$88.25	$92.15	$105.67	$103.83	$110.05	See Web	

RG405/U Coax, 50 Ohm

Part No. PE33191				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	47
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$85.16	$89.12	$84.80	$88.56	$96.14	$103.67	See Web	

SMA FEMALE 2 HOLE FLANGE TO SMP FEMALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE3W05930				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	48
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$87.45	$109.60	$121.27	$132.91	$144.55	$106.91	See Web	

SMA FEMALE 2 HOLE FLANGE TO SMP FEMALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W05557				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	49
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$116.97	$126.68	$136.40	$146.13	$155.87	$123.20	See Web	

SMA FEMALE 4 HOLE FLANGE TO MMCX PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C0064				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	50
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		
12"	24"	36"	48"	60"	-	Custom Len.	
$107.58	$102.31	$103.14	$103.99	$104.82	-	See Web	

SMA FEMALE 4 HOLE FLANGE TO SMA FEMALE 4 HOLE FLANGE



SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE35112				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	51
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$112.85	$112.27	$116.12	$120.01	$127.76	$135.50	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE35110				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	52
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$101.00	$105.02	$107.53	$111.49	$119.37	$127.32	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE35116				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	53
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$106.03	$110.83	$110.34	$116.13	$127.74	$139.33	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE35118				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	54
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$122.19	$129.53	$135.52	$133.28	$144.39	$155.48	See Web	

RG402/U Coax, 50 Ohm

Part No. PE33502				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	55
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	650 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$109.55	$109.55	$113.52	$124.60	$133.09	$142.07	See Web	

RG405/U Coax, 50 Ohm

Part No. PE3223				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	56
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$108.94	$108.94	$119.52	$123.54	$123.85	$131.29	See Web	

SMB PLUG TO BNC MALE

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3242				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	57
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.86	$54.26	$55.16	$56.11	$57.03	$57.93	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3349				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	58
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$52.85	$59.05	$65.73	$72.82	$74.61	$86.43	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3318				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	59
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$42.08	$42.72	$43.38	$44.04	$44.69	$45.35	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE33825				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	60
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$64.95	$66.11	$67.28	$68.51	$69.70	-	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3C3428				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	61
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$47.49	$54.49	$52.40	$60.13	$62.91	$65.71	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

RG223/U Coax, 50 Ohm — 62

Part No. PE3236				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W
12"	24"	36"	48"	60"	72"	Custom Len.
$49.47	$52.91	$55.86	$59.48	$62.98	$66.47	See Web

RG316/U Coax, 50 Ohm — 63

Part No. PE3C3023				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
Call	Call	Call	Call	Call	Call	See Web

PE-P195 Coax, 50 Ohm — 64

Part No. PE37250				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W
12"	24"	36"	48"	60"	-	Custom Len.
$58.36	$68.89	$74.51	$84.26	$93.99	-	See Web

SMB PLUG TO N FEMALE

Standard Flexible Cable Assemblies

RG141A/U Coax, 50 Ohm — 65

Part No. PE3W04161				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.19" dia.	13 dB/100ft	650 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$63.23	$71.34	$79.45	$87.56	$95.67	$68.43	See Web

SMB PLUG TO SMB PLUG

Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm — 66

Part No. PE33837				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W
12"	24"	36"	48"	60"	-	Custom Len.
$63.64	$74.45	$85.36	$96.17	$107.05	-	See Web

Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm — 67

Part No. PE34488				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.101" dia.		
12"	24"	36"	48"	60"	72"	Custom Len.
$53.63	$66.26	$74.07	$75.79	$83.29	$90.88	See Web

RG58C/U Coax, 50 Ohm — 68

Part No. PE33650				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	72"	Custom Len.
$64.07	$70.09	$70.98	$66.49	$67.31	$68.10	See Web

RG142B/U Coax, 50 Ohm — 69

Part No. PE33652				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W
12"	24"	36"	48"	60"	72"	Custom Len.
$55.72	$67.98	$74.67	$74.02	$80.14	$95.37	See Web

RG174A/U Coax, 50 Ohm — 70

Part No. PE3853				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W
12"	24"	36"	48"	60"	72"	Custom Len.
$49.34	$49.81	$50.29	$50.78	$51.26	$51.74	See Web

RG178B/U Coax, 50 Ohm — 71

Part No. PE33165				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
12"	24"	36"	48"	60"	72"	Custom Len.
$62.61	$63.78	$64.95	$62.22	$67.36	$68.55	See Web

RG188A/U Coax, 50 Ohm — 72

Part No. PE3587				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$55.94	$58.68	$56.66	$59.11	$61.55	$69.91	See Web

RG188-DS Coax, 50 Ohm — 73

Part No. PE3721				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$53.62	$56.88	$60.61	$64.37	$68.10	$71.84	See Web

RG196A/U Coax, 50 Ohm — 74

Part No. PE3588				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W
12"	24"	36"	48"	60"	72"	Custom Len.
$60.61	$62.12	$67.35	$65.13	$70.58	$68.15	See Web

RG223/U Coax, 50 Ohm — 75

Part No. PE3166				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W
12"	24"	36"	48"	60"	72"	Custom Len.
$61.58	$65.01	$68.44	$67.67	$70.84	$74.05	See Web

RG316/U Coax, 50 Ohm — 76

Part No. PE3915				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$55.95	$59.38	$62.81	$66.46	$69.96	$73.47	See Web

RG316-DS Coax, 50 Ohm — 77

Part No. PE33704				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$54.79	$58.24	$61.67	$62.30	$65.52	$72.32	See Web

RG400/U Coax, 50 Ohm — 78

Part No. PE34269				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W
12"	24"	36"	48"	60"	72"	Custom Len.
$70.37	$78.50	$79.43	$87.12	$103.51	$102.56	See Web

SMB PLUG TO SMB PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm — 79

Part No. PE34490				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.101" dia.		
12"	24"	36"	48"	60"	72"	Custom Len.
$56.77	$64.30	$71.82	$79.43	$86.94	$94.52	See Web

RG58C/U Coax, 50 Ohm — 80

Part No. PE33666				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W
12"	24"	36"	48"	60"	72"	Custom Len.
$66.46	$67.28	$68.08	$68.89	$69.70	$70.51	See Web

RG142B/U Coax, 50 Ohm — 81

Part No. PE33668				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W
12"	24"	36"	48"	60"	72"	Custom Len.
$59.09	$65.23	$71.28	$77.44	$83.50	$89.58	See Web

RG174A/U Coax, 50 Ohm — 82

Part No. PE33175				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W
12"	24"	36"	48"	60"	72"	Custom Len.
$60.83	$61.31	$61.78	$68.85	$69.49	$70.14	See Web

RG178B/U Coax, 50 Ohm — 83

Part No. PE33356				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W
12"	24"	36"	48"	60"	72"	Custom Len.
$69.82	$70.85	$71.92	$72.98	$74.04	$75.08	See Web

RG188A/U Coax, 50 Ohm — 84

Part No. PE3592				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$58.18	$60.46	$62.85	$65.23	$67.55	$69.91	See Web

RG188-DS Coax, 50 Ohm — 85

Part No. PE33143				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.118" dia.	30 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$64.19	$67.93	$71.66	$75.39	$79.14	$82.88	See Web

RG196A/U Coax, 50 Ohm — 86

Part No. PE3593				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W
12"	24"	36"	48"	60"	72"	Custom Len.
$65.04	$66.48	$67.95	$69.37	$70.83	$72.28	See Web

RG223/U Coax, 50 Ohm — 87

Part No. PE33670				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W
12"	24"	36"	48"	60"	72"	Custom Len.
$56.26	$59.43	$67.60	$65.82	$69.06	$72.28	See Web

RG316/U Coax, 50 Ohm — 88

Part No. PE33672				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$59.09	$62.40	$65.69	$68.97	$72.28	$75.58	See Web

RG316-DS Coax, 50 Ohm — 89

Part No. PE34485				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W
12"	24"	36"	48"	60"	72"	Custom Len.
$63.76	$66.96	$70.15	$79.35	$76.56	$79.75	See Web

RG400/U Coax, 50 Ohm — 90

Part No. PE34481				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W
12"	24"	36"	48"	60"	72"	Custom Len.
$73.93	$81.66	$89.37	$97.11	$104.81	$110.98	See Web

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

SMB PLUG TO SMB JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm

Part No. PE34491				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.101" dia.			91
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.46	$64.03	$71.55	$79.09	$86.66	$94.19	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE34493				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	92
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.00	$73.81	$74.63	$75.42	$76.22	$77.04	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE34495				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	93
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.11	$83.81	$82.26	$88.38	$94.45	$100.59	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE33674				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	94
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.54	$57.18	$54.30	$58.49	$59.13	$55.73	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE33676				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	95
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.94	$59.34	$60.37	$61.44	$62.48	$68.87	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3591				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	96
12"	24"	36"	48"	60"	72"	Custom Len.	
$51.70	$59.09	$55.99	$58.29	$60.68	$62.99	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE34489				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	97
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.32	$65.17	$64.24	$67.98	$71.73	$75.46	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE3130				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	98
12"	24"	36"	48"	60"	72"	Custom Len.	
$58.71	$63.79	$61.73	$63.24	$64.73	$66.24	See Web	

RG223/U Coax, 50 Ohm

Part No. PE34497				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	99
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.21	$70.38	$73.61	$76.84	$80.01	$83.24	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34487				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	1
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.12	$60.58	$63.78	$66.99	$70.18	$73.38	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34483				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	2
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.29	$86.03	$93.73	$101.44	$107.67	$115.27	See Web	

SMB PLUG TO SMP FEMALE

Flexible Cable Assemblies

PE-P086 Coax, 50 Ohm

Part No. PE3C6787				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.104" dia.	21.7 dB/100ft		3
12"	24"	36"	48"	60"	50CM	Custom Len.	
$78.28	$87.44	$92.01	$101.17	$108.79	$79.57	See Web	

SMB PLUG TO SSMA MALE

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C7602				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	4
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.81	$68.06	$69.30	$70.54	$71.78	$67.60	See Web	

SMB PLUG RIGHT ANGLE TO BNC MALE

Standard Flexible Cable Assemblies

RG223/U Coax, 50 Ohm

Part No. PE3W06905				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	5
12"	24"	36"	48"	60"	50CM	Custom Len.	
$48.38	$51.98	$55.06	$58.62	$62.18	$50.67	See Web	

SMB PLUG RIGHT ANGLE TO SMA MALE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W03030				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	6
12"	24"	36"	48"	60"	50CM	Custom Len.	
$41.59	$42.21	$42.83	$43.45	$44.07	$41.98	See Web	

SMB PLUG RIGHT ANGLE TO SMB PLUG RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE39120				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	7
12"	24"	36"	48"	60"	-	Custom Len.	
$58.90	$59.75	$55.99	$56.72	$57.45	-	See Web	

Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm

Part No. PE34465				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.101" dia.			8
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.38	$74.17	$81.98	$89.76	$97.57	$105.37	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE33654				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	9
12"	24"	36"	48"	60"	72"	Custom Len.	
$75.62	$70.82	$71.64	$72.44	$73.25	$80.18	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE33656				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	10
12"	24"	36"	48"	60"	72"	Custom Len.	
$74.65	$80.94	$92.50	$93.55	$99.86	$111.62	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3916				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	11
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.85	$70.50	$65.63	$66.11	$66.57	$67.06	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE33350				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	12
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.24	$73.27	$74.34	$75.39	$76.45	$77.51	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3589				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	13
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.75	$76.16	$71.62	$74.07	$76.50	$78.94	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE34463				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	14
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.10	$71.84	$75.57	$79.32	$83.07	$86.80	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE3590				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	15
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.29	$68.74	$70.18	$71.62	$73.07	$74.51	See Web	

RG223/U Coax, 50 Ohm

Part No. PE33121				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	16
12"	24"	36"	48"	60"	72"	Custom Len.	
$71.51	$74.70	$77.88	$81.08	$84.27	$87.45	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3917				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	17
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.00	$77.95	$75.35	$85.02	$81.70	$92.02	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

RG316-DS Coax, 50 Ohm

Part No. PE33476				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	18
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.10	$76.53	$74.08	$77.28	$80.48	$83.68	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34461				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	19
12"	24"	36"	48"	60"	72"	Custom Len.	
$81.93	$85.02	$92.74	$100.47	$106.68	$114.29	See Web	

SMB PLUG RIGHT ANGLE TO SMB JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm

Part No. PE34479				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.101" dia.			20
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.09	$67.61	$75.21	$82.71	$90.29	$97.83	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE34469				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	21
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.16	$72.95	$73.75	$74.61	$75.38	$76.18	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE34471				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	22
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.48	$79.55	$85.70	$91.76	$97.89	$103.95	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE33261				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	23
12"	24"	36"	48"	60"	72"	Custom Len.	
$65.58	$66.06	$66.53	$67.02	$67.49	$67.97	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE34467				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	24
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.14	$63.91	$64.97	$66.01	$67.06	$68.13	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3594				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	25
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.38	$68.81	$71.25	$73.69	$76.13	$78.57	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE34477				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	26
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.00	$66.36	$69.98	$73.61	$77.24	$80.81	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE33682				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	27
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.25	$64.70	$66.15	$67.61	$69.06	$70.51	See Web	

RG223/U Coax, 50 Ohm

Part No. PE34473				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	28
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.57	$73.80	$76.99	$80.19	$83.45	$86.61	See Web	

RG316/U Coax, 50 Ohm

Part No. PE33675				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	29
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.45	$65.74	$69.06	$72.35	$75.64	$86.21	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE33349				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	30
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.33	$71.99	$68.79	$72.03	$75.26	$78.42	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34475				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	31
12"	24"	36"	48"	60"	72"	Custom Len.	
$88.33	$96.04	$103.77	$109.93	$117.55	$125.15	See Web	

SMB PLUG RIGHT ANGLE TO SSMB PLUG

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W04513				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	32
12"	24"	36"	48"	60"	50CM	Custom Len.	
$62.35	$62.97	$63.58	$64.20	$64.82	$62.12	See Web	

SMC PLUG TO 10-32 MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

RG196A/U Coax, 50 Ohm

Part No. PE3W00597				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.		78 W	33
12"	24"	36"	48"	60"	50CM	Custom Len.	
$79.01	$80.51	$82.01	$83.50	$85.00	$79.97	See Web	

SMC PLUG TO BNC MALE

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE3244				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	34
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.37	$56.18	$60.46	$57.78	$62.34	$59.42	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3425				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	35
12"	24"	36"	48"	60"	72"	Custom Len.	
$48.17	$48.82	$49.46	$46.06	$50.79	$47.03	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3C2578				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	36
12"	24"	36"	48"	60"	72"	Custom Len.	
$45.70	$48.16	$50.61	$53.09	$59.16	$57.47	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3238				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.209" dia.	13.41 dB/100ft	50 W	37
12"	24"	36"	48"	60"	72"	Custom Len.	
$46.48	$49.43	$52.38	$55.33	$58.29	$61.24	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C2599				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	38
12"	24"	36"	48"	60"	72"	Custom Len.	
$47.42	$50.89	$54.36	$57.49	$56.36	$59.52	See Web	

SMC PLUG TO MCX PLUG

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W04152				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		39
12"	24"	36"	48"	60"	127CM	Custom Len.	
$38.04	$38.84	$39.67	$40.49	$41.31	Call	See Web	

SMC PLUG TO SMA MALE

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W04200				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		40
12"	24"	36"	48"	60"	50CM	Custom Len.	
$44.04	$44.86	$45.68	$46.49	$47.31	$44.58	See Web	

SMC PLUG TO SMC PLUG

Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm

Part No. PE34501				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.101" dia.			41
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.57	$60.61	$68.19	$75.71	$83.29	$90.82	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE33641				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	42
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.44	$70.24	$71.10	$71.88	$72.68	$73.48	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3490				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	43
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.42	$72.48	$78.55	$84.68	$90.77	$96.89	See Web	

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

See Our Website For Current Pricing & Real-Time Stock Availability!

RG174A/U Coax, 50 Ohm

Part No. PE3883				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	44
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$51.09	$55.31	$55.95	$52.55	$53.03	$53.51	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE3902				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	45
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.19	$62.23	$63.29	$69.63	$65.40	$66.46	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3595				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	46
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.80	$54.13	$56.58	$59.02	$61.46	$63.90	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE33154				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	47
1 piece price shown. See web or call for volume pricing.				0.118" dia.	30 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$49.59	$53.25	$56.38	$60.02	$63.64	$67.21	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE3596				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	48
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$57.05	$58.51	$59.94	$61.40	$62.85	$64.30	See Web	

RG223/U Coax, 50 Ohm

Part No. PE33647				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	49
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.34	$70.52	$73.71	$76.90	$80.09	$83.27	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3808				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	50
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.13	$62.57	$66.00	$69.63	$66.46	$69.63	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34721				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	51
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.11	$56.82	$60.01	$63.21	$66.41	$74.35	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34494				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	52
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$74.61	$82.32	$90.02	$97.77	$105.48	$111.63	See Web	

SMC PLUG TO SMC PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm

Part No. PE34502				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	53
1 piece price shown. See web or call for volume pricing.				0.101" dia.			
12"	24"	36"	48"	60"	72"	Custom Len.	
$58.10	$65.61	$73.21	$80.75	$88.33	$95.84	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE33658				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	54
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.75	$74.51	$75.38	$76.18	$76.99	$77.79	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE33660				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	55
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.44	$70.57	$76.65	$82.71	$88.85	$94.92	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE33556				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	56
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.40	$64.04	$58.62	$59.09	$59.62	$60.09	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE34492				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	57
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.27	$73.80	$69.36	$70.42	$71.47	$72.53	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3600				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	58
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.24	$66.69	$76.14	$71.57	$74.02	$76.45	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE34499				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	59
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.73	$64.37	$68.00	$71.62	$75.26	$78.82	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE3601				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	60
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.67	$64.10	$65.56	$67.01	$68.47	$69.91	See Web	

RG223/U Coax, 50 Ohm

Part No. PE33664				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	61
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$65.24	$68.41	$71.60	$74.78	$77.98	$81.17	See Web	

RG316/U Coax, 50 Ohm

Part No. PE33363				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	62
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.16	$69.70	$72.88	$76.06	$79.22	$82.39	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34518				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	63
1 piece price shown. See web or call for volume pricing.				0.114" dia.	26.1 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.33	$63.58	$66.81	$70.04	$73.28	$76.44	See Web	

RG400/U Coax, 50 Ohm

Part No. PE34496				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	64
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$79.28	$87.00	$94.73	$102.43	$108.63	$116.23	See Web	

SMC PLUG TO SMC JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm

Part No. PE34509				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	65
1 piece price shown. See web or call for volume pricing.				0.101" dia.			
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.46	$63.96	$71.55	$79.09	$86.61	$94.19	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE34503				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	66
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.41	$74.19	$75.04	$75.86	$76.65	$77.44	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE34505				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	67
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.11	$78.23	$84.29	$90.44	$96.49	$102.56	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE33580				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	68
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.84	$54.33	$54.30	$54.78	$55.26	$55.73	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE33352				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	69
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$75.80	$81.50	$77.89	$78.96	$80.00	$81.06	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE33686				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	70
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$51.70	$54.12	$55.93	$58.29	$60.61	$62.99	See Web	

RG188-DS Coax, 50 Ohm

Part No. PE34500				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	71
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$52.98	$56.11	$59.75	$63.37	$66.95	$70.57	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE33688				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	72
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$71.88	$73.35	$74.78	$76.25	$77.69	$79.15	See Web	

RG223/U Coax, 50 Ohm

Part No. PE34507				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	73
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.25	$72.41	$75.64	$78.82	$82.05	$85.28	See Web	

RG316/U Coax, 50 Ohm

Part No. PE33690				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	74
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.34	$55.44	$58.77	$62.05	$65.36	$68.65	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34511				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	75
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.28	$65.33	$62.68	$72.41	$69.08	$72.28	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

RG400/U Coax, 50 Ohm							
Part No. PE34498				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	76
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$80.34	$88.07	$95.76	$103.50	$109.68	$117.29	See Web	

SMC PLUG RIGHT ANGLE TO BNC MALE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm							
Part No. PE3C1988				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	77
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$53.32	$51.91	$52.53	$53.15	$53.77	$51.68	See Web	

SMC PLUG RIGHT ANGLE TO SMC PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm							
Part No. PE34466				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	78
1 piece price shown. See web or call for volume pricing.				0.101" dia.			
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.11	$70.64	$78.23	$85.76	$93.34	$100.87	See Web	
RG58C/U Coax, 50 Ohm							
Part No. PE33643				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	79
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.16	$77.96	$78.76	$79.58	$88.52	$81.19	See Web	
RG142B/U Coax, 50 Ohm							
Part No. PE33645				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	80
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.11	$75.21	$81.33	$87.40	$93.46	$99.62	See Web	
RG174A/U Coax, 50 Ohm							
Part No. PE3918				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	81
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.93	$69.41	$69.89	$70.37	$70.83	$77.69	See Web	
RG178B/U Coax, 50 Ohm							
Part No. PE3765				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	82
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$71.46	$72.62	$68.27	$69.34	$70.40	$71.45	See Web	
RG188A/U Coax, 50 Ohm							
Part No. PE3597				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	83
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.66	$66.87	$69.20	$71.55	$73.93	$76.25	See Web	
RG188-DS Coax, 50 Ohm							
Part No. PE34464				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	84
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$65.74	$69.37	$73.01	$76.65	$80.28	$83.83	See Web	
RG196A/U Coax, 50 Ohm							
Part No. PE3598				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	85
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.65	$63.11	$64.56	$66.01	$67.45	$68.92	See Web	
RG223/U Coax, 50 Ohm							
Part No. PE33649				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	86
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.21	$69.44	$72.61	$75.86	$79.03	$82.26	See Web	
RG316/U Coax, 50 Ohm							
Part No. PE3919				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	87
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.05	$75.23	$78.40	$81.57	$84.74	$87.92	See Web	
RG316-DS Coax, 50 Ohm							
Part No. PE34462				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	88
1 piece price shown. See web or call for volume pricing.				0.114" dia.	26.1 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$65.36	$68.58	$71.82	$75.04	$78.29	$81.45	See Web	
RG400/U Coax, 50 Ohm							
Part No. PE34459				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	89
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.29	$85.02	$92.74	$100.47	$106.68	$114.29	See Web	

SMC PLUG RIGHT ANGLE TO SMC JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm							
Part No. PE34486				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	90
1 piece price shown. See web or call for volume pricing.				0.101" dia.			
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.46	$68.97	$76.58	$84.09	$91.61	$99.22	See Web	
RG58C/U Coax, 50 Ohm							
Part No. PE34476				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	91
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.69	$78.49	$79.34	$80.14	$80.93	$81.72	See Web	
RG142B/U Coax, 50 Ohm							
Part No. PE34478				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	92
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.18	$76.25	$82.38	$88.45	$94.58	$100.66	See Web	
RG174A/U Coax, 50 Ohm							
Part No. PE34078				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	93
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.00	$61.46	$62.00	$62.45	$62.90	$63.45	See Web	
RG178B/U Coax, 50 Ohm							
Part No. PE34470				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	94
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.17	$78.23	$79.28	$80.34	$81.39	$82.43	See Web	
RG188A/U Coax, 50 Ohm							
Part No. PE3602				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	95
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.85	$65.23	$67.55	$69.91	$72.22	$74.61	See Web	
RG188-DS Coax, 50 Ohm							
Part No. PE34484				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	96
1 piece price shown. See web or call for volume pricing.				0.122" dia.	30 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.10	$67.72	$71.36	$74.99	$78.55	$82.18	See Web	
RG196A/U Coax, 50 Ohm							
Part No. PE33692				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	97
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.56	$79.03	$80.46	$81.94	$83.38	$84.83	See Web	
RG223/U Coax, 50 Ohm							
Part No. PE34480				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	98
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$67.29	$70.51	$73.68	$76.90	$80.14	$83.29	See Web	
RG316/U Coax, 50 Ohm							
Part No. PE34472				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	99
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.78	$67.06	$70.38	$73.68	$76.99	$80.28	See Web	
RG316-DS Coax, 50 Ohm							
Part No. PE34474				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	1
1 piece price shown. See web or call for volume pricing.				0.114" dia.	26.1 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.69	$66.95	$70.18	$73.41	$76.58	$79.80	See Web	
RG400/U Coax, 50 Ohm							
Part No. PE34482				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	2
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$85.02	$92.74	$100.47	$106.68	$114.29	$121.90	See Web	

SMC PLUG RIGHT ANGLE TO TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm							
Part No. PE3W05426				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	3
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.64	$64.87	$66.12	$67.36	$68.61	$64.43	See Web	

SMC JACK BULKHEAD TO UMCX PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

RG178B/U Coax, 50 Ohm

Part No. PE39035				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	4
3"	6"	9"	12"	18"	24"	Custom Len.	
$82.15	$82.15	$82.15	$82.15	$82.68	$83.22	See Web	

SMP MALE BULKHEAD TO SMA MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W05498				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	5
12"	24"	36"	48"	60"	50CM	Custom Len.	
$82.86	$92.69	$102.54	$110.83	$120.54	$89.16	See Web	

SMP MALE BULKHEAD TO SMP FEMALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C7572				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	6
12"	24"	36"	48"	60"	50CM	Custom Len.	
$113.03	$122.75	$132.46	$142.18	$151.90	$119.25	See Web	

SMP FEMALE TO SMA MALE

Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE36162				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	7
12"	24"	36"	48"	60"	72"	Custom Len.	
$100.94	$111.53	$122.94	$134.04	$148.46	$160.68	See Web	

Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE36168				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	8
12"	24"	36"	48"	60"	72"	Custom Len.	
$91.59	$104.06	$114.92	$121.63	$140.47	$144.82	See Web	

Part No. PE3W07044				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	9
12"	24"	36"	48"	60"	50CM	Custom Len.	
$55.41	$68.25	$81.09	$93.93	$106.76	$63.64	See Web	

SMP FEMALE TO SMP FEMALE

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE36148				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	10
12"	24"	36"	48"	60"	72"	Custom Len.	
$106.87	$108.81	$116.78	$124.79	$132.79	$140.77	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE36152				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	11
12"	24"	36"	48"	60"	72"	Custom Len.	
$82.70	$95.17	$100.78	$110.64	$121.90	$133.17	See Web	

Part No. PE3C4341				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	12
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.01	$81.84	$94.68	$107.53	$118.70	$77.24	See Web	

Standard Flexible Cable Assemblies

PE-P047 Coax, 50 Ohm

Part No. PE3C0757				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.056" dia.	35 dB/100ft	43 W	13
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.64	$79.35	$87.90	$96.44	$104.98	$76.27	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE36146				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	14
12"	24"	36"	48"	60"	72"	Custom Len.	
$110.21	$122.20	$126.18	$137.26	$148.37	$159.46	See Web	

RG405/U Coax, 50 Ohm

Part No. PE36150				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	15
12"	24"	36"	48"	60"	72"	Custom Len.	
$115.48	$123.54	$88.52	$130.56	$103.16	$108.94	See Web	

SMP FEMALE TO SMP FEMALE RIGHT ANGLE

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE36156				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	16
12"	24"	36"	48"	60"	72"	Custom Len.	
$101.37	$107.72	$115.47	$123.20	$130.95	$138.69	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE36160				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	17
12"	24"	36"	48"	60"	72"	Custom Len.	
$95.38	$107.13	$124.28	$128.82	$140.43	$152.01	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C0438				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	18
6"	9"	12"	18"	24"	-	Custom Len.	
$88.89	$91.95	$94.23	$93.15	$103.62	-	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE36154				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	19
12"	24"	36"	48"	60"	72"	Custom Len.	
$104.49	$121.22	$124.50	$135.30	$146.05	$156.85	See Web	

RG405/U Coax, 50 Ohm

Part No. PE36158				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	20
12"	24"	36"	48"	60"	72"	Custom Len.	
$91.04	$98.59	$106.13	$112.12	$119.55	$127.01	See Web	

SMP FEMALE RIGHT ANGLE TO BNC MALE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W06234				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	21
12"	18"	24"	36"	48"	60"	Custom Len.	
$45.49	$44.08	$44.38	$44.98	$45.58	$46.18	See Web	

SMP FEMALE RIGHT ANGLE TO MMCX PLUG RIGHT ANGLE

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C3221				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	22
12"	50CM	24"	36"	100CM	48"	Custom Len.	
$78.89	$80.27	$83.54	$92.66	$95.22	$101.77	See Web	

SMP FEMALE RIGHT ANGLE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W05673				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		23
12"	24"	36"	48"	60"	50CM	Custom Len.	
$58.77	$59.55	$60.34	$61.15	$61.94	$59.26	See Web	

SMP FEMALE RIGHT ANGLE TO SMA MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W05056				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		24
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.07	$66.67	$70.28	$73.88	$77.49	$65.38	See Web	

SMP FEMALE RIGHT ANGLE TO SMA FEMALE

Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE3W05740				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	25
12"	24"	36"	48"	60"	50CM	Custom Len.	
$77.08	$89.93	$102.77	$114.00	$126.65	$85.30	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

SMP FEMALE RIGHT ANGLE TO SMA FEMALE 2 HOLE FLANGE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE3W05692				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	26
12"	18"	24"	36"	48"	60"	Custom Len.	
$119.91	$121.02	$126.63	$137.84	$149.05	$160.27	See Web	

SMP FEMALE RIGHT ANGLE TO SMP FEMALE

Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE3W03777				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	27
12"	24"	36"	48"	60"	50CM	Custom Len.	
$84.10	$96.95	$108.26	$120.93	$133.58	$92.33	See Web	

SMP FEMALE RIGHT ANGLE TO SMP FEMALE RIGHT ANGLE

Standard Flexible Cable Assemblies

PE-P047 Coax, 50 Ohm

Part No. PE3C4969				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.056" dia.	35 dB/100ft	43 W	28
12"	50CM	24"	36"	100CM	48"	Custom Len.	
$111.74	$112.53	$115.55	$123.97	$126.34	$132.40	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE3W04802				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	29
12"	24"	36"	48"	60"	50CM	Custom Len.	
$63.45	$75.27	$87.07	$98.89	$109.17	$71.01	See Web	

SMP FEMALE RIGHT ANGLE TO REVERSE POLARITY TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W05481				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		30
12"	24"	36"	48"	60"	50CM	Custom Len.	
$91.19	$91.98	$92.78	$93.58	$94.38	$91.70	See Web	

SSMA MALE TO SSMA MALE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3673				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	31
6"	12"	18"	24"	36"	48"	Custom Len.	
$70.51	$70.69	$70.97	$71.23	$71.71	$72.22	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE33762				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	32
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.76	$80.76	$81.29	$86.76	$82.87	$89.15	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE33700				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	33
12"	24"	36"	48"	60"	-	Custom Len.	
$67.72	$69.98	$72.22	$74.45	$76.65	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE33071				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		34
6"	12"	18"	24"	36"	48"	Custom Len.	
$79.43	$79.43	$81.00	$82.59	$85.77	$88.94	See Web	

SSMA MALE TO SSMA MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36569				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	35
6"	12"	18"	24"	36"	48"	Custom Len.	
$74.51	$82.27	$75.04	$75.26	$75.79	$76.25	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36571				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	36
6"	12"	18"	24"	36"	48"	Custom Len.	
$105.81	$106.34	$106.85	$107.39	$106.93	$108.00	See Web	

RG316/U Coax, 50 Ohm

Part No. PE36573				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	37
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.54	$77.56	$79.20	$80.86	$84.16	$87.46	See Web	

SSMA MALE RIGHT ANGLE TO SSMA MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36570				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	38
6"	12"	18"	24"	36"	48"	Custom Len.	
$78.62	$78.82	$79.09	$79.34	$79.80	$80.28	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE36572				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	39
6"	12"	18"	24"	36"	48"	Custom Len.	
$134.07	$134.59	$135.13	$135.64	$136.66	$137.72	See Web	

RG316/U Coax, 50 Ohm

Part No. PE36574				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	40
6"	12"	18"	24"	36"	48"	Custom Len.	
$80.01	$81.66	$83.29	$84.96	$88.25	$91.55	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE38407				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	41
12"	24"	36"	48"	60"	-	Custom Len.	
$76.25	$79.28	$82.26	$85.22	$88.25	-	See Web	

SSMB PLUG TO SMA MALE

Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W05115				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		42
12"	24"	36"	48"	60"	50CM	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

Standard Flexible Cable Assemblies

RG188-DS Coax, 50 Ohm

Part No. PE3W06018				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.118" dia.	30 dB/100ft	160 W	43
12"	24"	36"	48"	60"	50CM	Custom Len.	
$56.07	$60.14	$64.21	$68.27	$72.34	$58.68	See Web	
Part No. PE3W06717				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.118" dia.	30 dB/100ft	160 W	44
12"	24"	36"	48"	60"	50CM	Custom Len.	
$87.00	$91.07	$95.13	$99.20	$103.16	$89.60	See Web	

SSMB PLUG TO SSMB PLUG

Standard Flexible Cable Assemblies

RG188-DS Coax, 50 Ohm

Part No. PE3W06017				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.118" dia.	30 dB/100ft	160 W	45
12"	24"	36"	48"	60"	50CM	Custom Len.	
$79.71	$83.78	$87.84	$91.91	$95.98	$82.31	See Web	

RG196A/U Coax, 50 Ohm

Part No. PE3122				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W	46
12"	24"	36"	48"	60"	72"	Custom Len.	
$83.65	$91.90	$86.65	$88.18	$89.68	$91.18	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3139				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		47
12"	24"	36"	48"	60"	72"	Custom Len.	
$96.49	$99.93	$95.70	$98.88	$102.05	$105.23	See Web	

SSMB PLUG RIGHT ANGLE TO SSMB PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

See Our Website For Current Pricing & Real-Time Stock Availability!

RG178B/U Coax, 50 Ohm

Part No. PE3C4801				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$61.22	$60.00	$61.13	$62.26	$63.38	$59.58	See Web

48

RG196A/U Coax, 50 Ohm

Part No. PE3134				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.08" dia.	49 dB/100ft	78 W
12"	24"	36"	48"	60"	72"	Custom Len.
$71.38	$72.90	$74.40	$75.91	$77.42	$78.92	See Web

49

RG316/U Coax, 50 Ohm

Part No. PE3157				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	
12"	24"	36"	48"	60"	72"	Custom Len.
$93.77	$97.20	$94.82	$97.97	$107.78	$104.33	See Web

50

SSMC PLUG TO SMB JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3W08023				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
12"	18"	24"	36"	48"	60"	Custom Len.
$70.14	$68.11	$68.71	$69.91	$71.11	$72.31	See Web

51

SSMC PLUG TO SSMC PLUG

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4419				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
6"	12"	18"	24"	36"	48"	Custom Len.
$71.31	$78.91	$72.14	$72.54	$73.35	$74.16	See Web

52

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4441				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	18"	24"	36"	48"	Custom Len.
$78.77	$82.92	$87.06	$91.19	$99.46	$107.75	See Web

53

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4388				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
6"	12"	18"	24"	36"	48"	Custom Len.
$86.64	$87.21	$87.79	$83.28	$84.32	$85.34	See Web

54

RG316/U Coax, 50 Ohm

Part No. PE3C4403				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
6"	12"	18"	24"	36"	48"	Custom Len.
$77.71	$79.26	$80.81	$82.32	$85.42	$88.49	See Web

55

SSMC PLUG TO SSMC PLUG RIGHT ANGLE

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4420				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
6"	12"	18"	24"	36"	48"	Custom Len.
$67.55	$67.96	$68.36	$68.77	$69.58	$70.39	See Web

56

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4481				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	18"	24"	36"	48"	Custom Len.
$75.37	$79.51	$83.66	$87.79	$96.06	$104.33	See Web

57

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4455				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
6"	12"	18"	24"	36"	48"	Custom Len.
$72.48	$73.01	$73.53	$74.05	$75.05	$76.09	See Web

58

RG316/U Coax, 50 Ohm

Part No. PE3C4404				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W
6"	12"	18"	24"	36"	48"	Custom Len.
$73.93	$80.01	$77.03	$78.55	$81.65	$84.71	See Web

59

SSMC PLUG TO SSMC JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4442				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	18"	24"	36"	48"	Custom Len.
$78.41	$82.97	$79.57	$83.70	$91.97	$96.68	See Web

60

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4389				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
6"	12"	18"	24"	36"	48"	Custom Len.
$77.37	$85.68	$78.41	$78.92	$79.95	$89.26	See Web

61

SSMC PLUG TO SSMC JACK RIGHT ANGLE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4459				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
6"	12"	18"	24"	36"	48"	Custom Len.
$74.69	$75.22	$75.71	$76.22	$77.26	$78.28	See Web

62

SSMC PLUG TO TNC MALE

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4434				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
6"	12"	18"	24"	36"	48"	Custom Len.
$59.56	$59.98	$60.37	$60.78	$61.59	$62.41	See Web

63

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4453				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	18"	24"	36"	48"	Custom Len.
$65.82	$69.96	$74.10	$78.23	$86.50	$94.79	See Web

64

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4401				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
6"	12"	18"	24"	36"	48"	Custom Len.
$71.52	$72.04	$72.55	$73.06	$74.09	$75.10	See Web

65

RG316/U Coax, 50 Ohm

Part No. PE3C4417				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.098" dia.	58 dB/100ft	160 W
6"	12"	18"	24"	36"	48"	Custom Len.
$71.20	$72.74	$74.30	$75.82	$78.91	$81.99	See Web

66

SSMC PLUG RIGHT ANGLE TO SMA MALE

Standard Flexible Cable Assemblies

RG188-DS Coax, 50 Ohm

Part No. PE3W04994				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.118" dia.	30 dB/100ft	160 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$64.29	$68.34	$72.41	$76.48	$80.54	$66.89	See Web

67

SSMC PLUG RIGHT ANGLE TO SSMC PLUG RIGHT ANGLE

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4421				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft	
6"	12"	18"	24"	36"	48"	Custom Len.
$63.77	$64.19	$64.58	$65.00	$65.81	$66.61	See Web

68

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4482				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
6"	12"	18"	24"	36"	48"	Custom Len.
$71.97	$76.11	$80.26	$84.39	$92.65	$100.94	See Web

69

See Our Website For Current Pricing & Real-Time Stock Availability!

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4457				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	70
6"	12"	18"	24"	36"	48"	Custom Len.	
$63.25	$63.77	$64.28	$64.79	$65.82	$66.84	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4374				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	71
6"	12"	18"	24"	36"	48"	Custom Len.	
$70.15	$71.71	$73.25	$74.77	$77.87	$80.94	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4470				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	85 W	72
6"	12"	18"	24"	36"	48"	Custom Len.	
$73.61	$75.27	$72.58	$74.13	$77.24	$80.34	See Web	

SSMC PLUG RIGHT ANGLE TO SSMC JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4483				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	73
6"	12"	18"	24"	36"	48"	Custom Len.	
$67.88	$72.02	$76.16	$80.29	$88.55	$96.84	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4458				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	74
6"	12"	18"	24"	36"	48"	Custom Len.	
$68.13	$75.52	$69.16	$69.68	$70.69	$71.73	See Web	

SSMC PLUG RIGHT ANGLE TO SSMC JACK RIGHT ANGLE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4460				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	75
6"	12"	18"	24"	36"	48"	Custom Len.	
$65.43	$65.95	$66.47	$66.99	$68.00	$69.04	See Web	

SSMC PLUG RIGHT ANGLE TO TNC MALE

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3C4435				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		76
6"	12"	18"	24"	36"	48"	Custom Len.	
$55.78	$61.81	$56.60	$57.02	$57.81	$58.62	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4490				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	77
6"	12"	18"	24"	36"	48"	Custom Len.	
$62.42	$66.54	$70.69	$74.82	$83.11	$91.37	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4468				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	78
6"	12"	18"	24"	36"	48"	Custom Len.	
$62.27	$62.79	$63.30	$63.82	$64.84	$65.86	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C4418				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	58 dB/100ft	160 W	79
6"	12"	18"	24"	36"	48"	Custom Len.	
$67.42	$68.96	$70.52	$72.04	$75.15	$78.21	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE3C4480				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.114" dia.	9.15 dB/100ft	85 W	80
6"	12"	18"	24"	36"	48"	Custom Len.	
$66.74	$68.28	$69.85	$71.39	$74.49	$77.61	See Web	

SSMC PLUG RIGHT ANGLE TO TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3W05518				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.		55 W	81
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.20	$67.43	$68.67	$69.92	$71.17	$66.99	See Web	

SSMC JACK BULKHEAD TO SSMC JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4443				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	82
6"	12"	18"	24"	36"	48"	Custom Len.	
$63.78	$67.93	$72.06	$76.19	$84.46	$92.74	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4390				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	83
6"	12"	18"	24"	36"	48"	Custom Len.	
$73.00	$73.53	$74.05	$74.57	$75.57	$76.60	See Web	

SSMC JACK BULKHEAD TO SSMC JACK RIGHT ANGLE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4461				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	84
6"	12"	18"	24"	36"	48"	Custom Len.	
$70.32	$70.83	$71.35	$71.86	$72.89	$73.90	See Web	

SSMC JACK BULKHEAD TO TNC MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3C4454				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	85
6"	12"	18"	24"	36"	48"	Custom Len.	
$58.31	$62.46	$66.60	$70.72	$79.01	$87.27	See Web	

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4402				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	86
6"	12"	18"	24"	36"	48"	Custom Len.	
$67.14	$67.67	$68.19	$68.70	$69.72	$70.73	See Web	

SSMC JACK RIGHT ANGLE BULKHEAD TO SSMC JACK RIGHT ANGLE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3C4462				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W	87
6"	12"	18"	24"	36"	48"	Custom Len.	
$67.62	$74.97	$75.54	$69.18	$70.19	$71.22	See Web	

TNC MALE TO BNC MALE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE37885				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	88
12"	24"	36"	48"	60"	-	Custom Len.	
$34.32	$35.11	$35.91	$39.71	$40.60	-	See Web	

PE-C200 Coax, 50 Ohm

Part No. PE36068				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10.8 dB/100ft	170 W	89
12"	24"	36"	48"	60"	-	Custom Len.	
$50.91	$55.06	$59.70	$64.37	$68.97	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE37594				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	90
12"	24"	36"	48"	60"	-	Custom Len.	
$45.71	$46.25	$49.38	$52.44	$55.06	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE37563				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	91
12"	24"	36"	48"	60"	-	Custom Len.	
$90.82	$92.22	$93.62	$94.98	$96.36	-	See Web	

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE34504				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	92
12"	24"	36"	48"	60"	72"	Custom Len.	
$79.01	$82.12	$85.23	$88.35	$91.46	$94.57	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3497				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	93
12"	24"	36"	48"	60"	72"	Custom Len.	
$41.20	$42.11	$43.01	$41.34	$42.16	$45.81	See Web	

RG58-P Coax, 50 Ohm

Part No. PE35789				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.159" dia.	17.3 dB/100ft	632 W	94
12"	24"	36"	48"	60"	-	Custom Len.	
$54.60	$60.09	$65.59	$71.08	$76.58	-	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3551				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	95
12"	24"	36"	48"	60"	72"	Custom Len.	
$44.80	$51.16	$60.41	$63.30	$69.60	$75.91	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3C3400				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	96
12"	24"	36"	48"	60"	72"	Custom Len.	
$49.26	$49.75	$50.22	$50.67	$51.17	$51.63	See Web	

RG178B/U Coax, 50 Ohm

Part No. PE39255				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	97
12"	24"	36"	48"	60"	-	Custom Len.	
$73.26	$76.25	$83.45	$90.63	$97.77	-	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3C3401				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	98
12"	24"	36"	48"	60"	72"	Custom Len.	
$51.05	$53.35	$61.13	$57.37	$59.66	$61.89	See Web	

RG213/U Coax, 50 Ohm

Part No. PE33969				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	99
12"	24"	36"	48"	60"	72"	Custom Len.	
$79.21	$81.05	$82.87	$84.70	$86.52	$88.36	See Web	

RG214/U Coax, 50 Ohm

Part No. PE33701				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	1
12"	24"	36"	48"	60"	72"	Custom Len.	
$90.68	$98.73	$106.78	$113.26	$121.19	$137.77	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3498				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	2
12"	24"	36"	48"	60"	72"	Custom Len.	
$40.90	$48.44	$51.91	$55.05	$53.77	$62.03	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C3393				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	3
12"	24"	36"	48"	60"	72"	Custom Len.	
$50.85	$54.06	$60.28	$63.91	$63.09	$66.26	See Web	

RG393/U Coax, 50 Ohm

Part No. PE37859				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W	4
12"	24"	36"	48"	60"	-	Custom Len.	
$83.50	$106.56	$113.64	$129.32	$144.94	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE33535				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	5
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.97	$64.82	$68.79	$81.53	$89.84	$98.12	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE37478				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	6
12"	24"	36"	48"	60"	-	Custom Len.	
$45.32	$54.45	$62.90	$71.88	$80.86	-	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3CA1091				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.			7
12"	24"	36"	48"	60"	72"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

RG55B/U Coax, 53 Ohm

Part No. PE3904				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	8
12"	24"	36"	48"	60"	72"	Custom Len.	
$40.72	$43.19	$45.68	$48.17	$50.67	$53.15	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3023				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	9
12"	24"	36"	48"	60"	72"	Custom Len.	
$39.08	$42.58	$43.72	$42.28	$43.34	$47.30	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE34510				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	10
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.31	$55.44	$58.10	$60.68	$63.30	$65.88	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE34508				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	11
12"	24"	36"	48"	60"	72"	Custom Len.	
$36.00	$37.46	$38.94	$40.41	$41.85	$43.33	See Web	

TNC MALE TO MINI UHF MALE

Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3C0047				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		12
12"	24"	36"	48"	60"	-	Custom Len.	
$33.28	$34.11	$34.94	$35.76	$36.60	-	See Web	

TNC MALE TO N MALE

Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3W01959				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		13
12"	24"	36"	48"	60"	50CM	Custom Len.	
$49.24	$50.05	$50.85	$51.66	$52.47	$49.75	See Web	

Low Loss Flexible Cable Assemblies

LMR-240 Coax, 50 Ohm

Part No. PE3W04201				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		14
12"	24"	36"	48"	60"	50CM	Custom Len.	
$44.95	$45.92	$46.91	$47.88	$48.86	$45.57	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0162				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			15
12"	18"	24"	36"	48"	60"	Custom Len.	
$410.26	$419.46	$428.65	$447.04	$465.41	$483.80	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0207				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			16
8"	12"	18"	24"	30"	36"	Custom Len.	
$383.46	$388.77	$396.74	$404.70	$412.68	$420.65	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0240				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			17
12"	18"	24"	36"	48"	60"	Custom Len.	
$448.95	$464.28	$479.64	$510.32	$541.00	$571.69	See Web	

TNC MALE TO N MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0164				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			18
12"	18"	24"	36"	48"	60"	Custom Len.	
$534.98	$544.17	$553.36	$571.74	$590.12	$608.51	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0209				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			19
8"	12"	18"	24"	30"	36"	Custom Len.	
$489.78	$495.07	$503.06	$511.01	$518.99	$526.95	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0242				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			20
12"	18"	24"	36"	48"	60"	Custom Len.	
$606.09	$621.42	$636.78	$667.46	$698.14	$728.83	See Web	

TNC MALE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0163				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			21
12"	18"	24"	36"	48"	60"	Custom Len.	
$504.81	$514.01	$523.19	$541.58	$559.96	$578.34	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

For Custom Lengths, Metric Lengths or Special Configurations, Please call (949) 261-1920

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0208				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			22
8"	12"	18"	24"	30"	36"	Custom Len.	
$494.03	$499.35	$507.32	$515.28	$523.26	$531.22	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0241				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			23
12"	18"	24"	36"	48"	60"	Custom Len.	
$530.98	$546.33	$561.68	$592.36	$623.04	$653.72	See Web	

TNC MALE TO SMA MALE

Low Loss Flexible Cable Assemblies

LMR-195-FR Coax, 50 Ohm

Part No. PE3W04028				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		24
12"	24"	36"	48"	60"	50CM	Custom Len.	
$31.02	$44.13	$45.24	$46.35	$47.44	$43.72	See Web	

TNC MALE TO SMA MALE RIGHT ANGLE

Flexible Cable Assemblies

LMR-200 Coax, 50 Ohm

Part No. PE3W07265				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10.5 dB/100ft		25
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.04	$66.82	$67.61	$68.39	$69.19	$66.53	See Web	

TNC MALE TO SMP FEMALE RIGHT ANGLE

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3W05738				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		26
12"	24"	36"	48"	60"	50CM	Custom Len.	
$57.43	$60.76	$69.23	$67.45	$70.79	$59.57	See Web	

TNC MALE TO TNC MALE

Flexible Cable Assemblies

LMR-195-FR Coax, 50 Ohm

Part No. PE3W05242				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		27
12"	24"	36"	48"	60"	50CM	Custom Len.	
$28.49	$29.59	$30.70	$31.81	$32.91	$29.20	See Web	

Flexible Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3C7891				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W	28
12"	24"	36"	48"	60"	50CM	Custom Len.	
$66.17	$66.78	$67.40	$68.01	$68.63	$65.94	See Web	

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE36555				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	29
12"	24"	36"	48"	60"	-	Custom Len.	
$42.98	$43.86	$40.67	$45.64	$46.53	-	See Web	

PE-C240 Coax, 50 Ohm

Part No. PE35997				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	9.2 dB/100ft	250 W	30
12"	24"	36"	48"	60"	-	Custom Len.	
$49.37	$47.65	$49.38	$52.44	$54.50	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE35886				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	31
12"	24"	36"	48"	60"	-	Custom Len.	
$99.92	$95.70	$99.46	$104.75	$106.59	-	See Web	

LMR-400-DB Coax, 50 Ohm

Part No. PE3W00572				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	4.15 dB/100ft		32
12"	24"	36"	48"	60"	50CM	Custom Len.	
$87.00	$88.59	$90.17	$91.75	$93.34	$88.01	See Web	

LMR-195 Coax, 50 Ohm

Part No. PE3C0042				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		33
12"	24"	36"	48"	60"	-	Custom Len.	
$39.81	$40.62	$41.47	$42.34	$43.19	-	See Web	

Part No. PE3C0117				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		34
12"	24"	36"	48"	60"	-	Custom Len.	
$57.91	$58.74	$59.56	$60.42	$58.97	-	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0159				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			35
12"	18"	24"	36"	48"	60"	Custom Len.	
$419.33	$428.52	$437.70	$456.09	$474.47	$492.86	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5249				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			36
12"	24"	36"	48"	60"	50CM	Custom Len.	
$222.74	$245.21	$267.66	$290.11	$312.56	$237.13	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0204				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			37
8"	12"	18"	24"	30"	36"	Custom Len.	
$397.61	$402.91	$410.89	$418.85	$426.83	$434.78	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0238				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			38
12"	18"	24"	36"	48"	60"	Custom Len.	
$444.62	$459.96	$475.31	$506.00	$536.67	$567.35	See Web	

Precision Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39479				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	39
6"	9"	12"	18"	24"	-	Custom Len.	
$58.88	Call	$63.20	Call	$56.46	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE39471				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	40
6"	9"	12"	18"	24"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P300LL Coax, 50 Ohm

Part No. PE334				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.	4.6 dB/100ft		41
12"	24"	36"	48"	60"	50CM	Custom Len.	
$340.49	$368.59	$396.73	$424.85	$452.96	$358.51	See Web	

PE-P142LL Coax, 50 Ohm

Part No. PE347				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		42
12"	24"	36"	48"	60"	50CM	Custom Len.	
$168.98	$186.58	$204.19	$221.79	$239.40	$180.26	See Web	

Standard Formable Cable Assemblies

PE-SR047FL Coax, 50 Ohm

Part No. PE34280				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.	36 dB/100ft	32 W	43
6"	12"	18"	24"	36"	48"	Custom Len.	
$87.84	$91.82	$95.70	$99.68	$107.54	$113.77	See Web	

PE-SR401FL Coax, 50 Ohm

Part No. PE34282				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					7.6 dB/100ft	1,400 W	44
6"	12"	18"	24"	36"	48"	Custom Len.	
$184.95	$184.95	$193.30	$201.65	$218.35	$235.06	See Web	

PE-SR402FL Coax, 50 Ohm

Part No. PE3466				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	45
6"	12"	18"	24"	36"	48"	Custom Len.	
$101.82	$101.82	$105.95	$108.57	$123.94	$133.22	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39493				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	46
-	6"	9"	12"	18"	24"	Custom Len.	
-	$62.88	Call	Call	Call	Call	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE3684				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	47
6"	12"	18"	24"	36"	48"	Custom Len.	
$89.91	$95.65	$101.32	$107.05	$116.75	$128.03	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39485				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W	48
6"	9"	12"	18"	24"	-	Custom Len.	
$55.86	$58.14	$60.41	$65.11	$59.63	-	See Web	

Standard Flexible Cable Assemblies

PE-B100 Coax, 50 Ohm

Part No. PE38830				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.101" dia.			49
12"	24"	36"	48"	60"	-	Custom Len.	
$64.83	$72.03	$79.20	$86.34	$93.62	-	See Web	

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

See Our Website For Current Pricing & Real-Time Stock Availability!

For our complete selection of cable assemblies, please visit our website

RG8A/U Coax, 50 Ohm

Part No. PE3418				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	50
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.35	$72.16	$75.21	$78.15	$81.19	$84.23	See Web	

RG8X Coax, 50 Ohm

Part No. PE35671				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	51
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13.5 dB/100ft	60 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$73.08	$76.97	$73.80	$76.90	$80.01	-	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3394				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	52
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
12"	18"	24"	30"	36"	48"	Custom Len.	
$41.12	$41.58	$42.02	$42.48	$42.93	$43.89	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3544				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	53
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.00	$59.20	$65.88	$72.96	$79.76	$86.59	See Web	

RG174A/U Coax, 50 Ohm

Part No. PE3425				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	54
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.63	$69.11	$74.03	$74.70	$70.54	$71.01	See Web	

RG188A/U Coax, 50 Ohm

Part No. PE3434				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	55
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.46	$71.89	$74.34	$76.77	$79.20	$81.65	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3421				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	56
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.46	$75.28	$77.10	$78.93	$80.76	$82.59	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3435				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	57
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$98.94	$111.85	$120.29	$129.22	$129.34	$146.42	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3414				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	58
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$51.64	$54.58	$58.00	$61.62	$65.12	$68.61	See Web	

RG303/U Coax, 50 Ohm

Part No. PE33013				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	59
1 piece price shown. See web or call for volume pricing.				0.17" dia.	14 dB/100ft	650 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$46.53	$53.68	$56.09	$62.41	$74.95	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3747				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	60
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.44	$73.62	$76.78	$86.59	$83.15	$93.59	See Web	

RG316-DS Coax, 50 Ohm

Part No. PE34316				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	61
1 piece price shown. See web or call for volume pricing.				0.114" dia.	30 dB/100ft	160 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$64.25	$67.45	$76.25	$73.84	$77.05	-	See Web	

RG393/U Coax, 50 Ohm

Part No. PE33185				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	62
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$105.10	$121.41	$131.30	$158.03	$164.84	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3608				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	63
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.86	$68.10	$79.11	$83.42	$96.02	$104.29	See Web	

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1043				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	64
1 piece price shown. See web or call for volume pricing.				0.163" dia.			
12"	24"	36"	50CM	100CM	-	Custom Len.	
Call	$321.79	$312.90	Call	Call	-	See Web	

PE-P195 Coax, 50 Ohm

Part No. PE35711				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	65
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.5 dB/100ft	650 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$53.85	$62.33	$77.62	$80.28	$89.32	-	See Web	

LMR-240 Coax, 50 Ohm

Part No. PE3CA1087				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	66
1 piece price shown. See web or call for volume pricing.				0.24" dia.			
12"	24"	36"	48"	60"	72"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

LMR-400-UF Coax, 50 Ohm

Part No. PE3W00808				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	67
1 piece price shown. See web or call for volume pricing.				0.405" dia.	5 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$88.31	$91.12	$93.93	$96.74	$99.55	$90.12	See Web	

LMR-600 Coax, 50 Ohm

Part No. PE3C0631				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	68
1 piece price shown. See web or call for volume pricing.				0.59" dia.	2.62 dB/100ft		
12"	24"	36"	48"	60"	72"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

RG55B/U Coax, 53 Ohm

Part No. PE3504				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	69
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$47.73	$50.22	$52.71	$54.69	$57.15	$59.62	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3402				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	70
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	
12"	18"	24"	30"	36"	48"	Custom Len.	
$41.53	$42.08	$45.19	$43.13	$43.67	$44.73	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE3430				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	71
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$69.73	$72.34	$74.94	$77.53	$80.14	$82.72	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE3408				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	72
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$42.05	$43.56	$48.83	$46.61	$48.14	$49.65	See Web	

M17/60-RG142-27478 Coax, 50 Ohm

Part No. PE3M0028				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	73
1 piece price shown. See web or call for volume pricing.				0.195" dia.			
12"	18"	24"	30"	36"	48"	Custom Len.	
$170.43	$173.38	$176.35	$179.30	$182.26	$188.17	See Web	

M17/84-RG223-0XDS2 Coax, 50 Ohm

Part No. PE3M0056				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	74
1 piece price shown. See web or call for volume pricing.				0.212" dia.			
12"	18"	24"	30"	36"	48"	Custom Len.	
$175.09	$180.37	$185.68	$190.96	$196.24	$206.83	See Web	

M17/128-RG400-27478 Coax, 50 Ohm

Part No. PE3M0084				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	75
1 piece price shown. See web or call for volume pricing.				0.195" dia.			
12"	18"	24"	30"	36"	48"	Custom Len.	
$172.05	$175.80	$179.57	$183.33	$187.09	$194.62	See Web	

M17/113-RG316-27478 Coax, 50 Ohm

Part No. PE3M0099				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	76
1 piece price shown. See web or call for volume pricing.				0.098" dia.			
6"	8"	12"	16"	18"	24"	Custom Len.	
$204.19	$204.55	$205.28	$205.95	$206.36	$207.46	See Web	

M17/119-RG174-0XDS2 Coax, 50 Ohm

Part No. PE3M0114				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	77
1 piece price shown. See web or call for volume pricing.				0.11" dia.			
6"	8"	12"	16"	18"	24"	Custom Len.	
$203.53	$203.66	$203.95	$204.23	$204.38	$204.80	See Web	

M17/28-RG058-0XDS2 Coax, 50 Ohm

Part No. PE3M0124				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	78
1 piece price shown. See web or call for volume pricing.				0.195" dia.			
12"	18"	24"	30"	36"	48"	Custom Len.	
$281.81	$282.45	$283.11	$283.75	$284.41	$285.70	See Web	

Standard Semi-Rigid Cable Assemblies

PE-047SR Coax, 50 Ohm

Part No. PE34273				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	79
1 piece price shown. See web or call for volume pricing.					40 dB/100ft	32 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$89.37	$94.86	$100.32	$105.76	$115.07	$125.82	See Web	

PE-SR047AL Coax, 50 Ohm

Part No. PE34277				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	80
1 piece price shown. See web or call for volume pricing.				0.047" dia.	41 dB/100ft	32 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$88.78	$93.62	$98.49	$103.31	$111.37	$120.94	See Web	

PE-SR402AL Coax, 50 Ohm

Part No. PE34279				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	81
1 piece price shown. See web or call for volume pricing.				0.141" dia.	13 dB/100ft	450 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$93.03	$98.03	$103.04	$106.55	$116.45	$126.31	See Web	

PE-SR405AL Coax, 50 Ohm

Part No. PE34284				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	82
1 piece price shown. See web or call for volume pricing.					23 dB/100ft	130 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$88.85	$93.40	$98.03	$102.65	$110.26	$119.37	See Web	

RG401/U Coax, 50 Ohm

Part No. PE34271				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	83
1 piece price shown. See web or call for volume pricing.					7.5 dB/100ft	870 W	
6"	12"	18"	24"	36"	48"	Custom Len.	
$187.57	$199.51	$192.95	$204.47	$227.57	$274.66	See Web	

For Custom Lengths, Metric Lengths or Special Configurations, Please call (949) 261-1920

See Our Website For Current Pricing & Real-Time Stock Availability!

RG402/U Coax, 50 Ohm

Part No. PE3074				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.1 dB/100ft	450 W	84
6"	12"	18"	24"	36"	48"	Custom Len.	
$101.52	$101.52	$105.52	$108.03	$123.08	$123.86	See Web	

RG405/U Coax, 50 Ohm

Part No. PE33391				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22 dB/100ft	130 W	85
6"	12"	18"	24"	36"	48"	Custom Len.	
$87.84	$91.55	$95.19	$98.88	$106.13	$111.87	See Web	

PE-SR401AL-STRAIGHT Coax, 50 Ohm

Part No. PE34275				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.25" dia.	8 dB/100ft	1,400 W	86
6"	12"	18"	24"	36"	48"	Custom Len.	
$167.84	$177.35	$186.90	$196.42	$215.48	$234.54	See Web	

TNC MALE TO TNC MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3C0058				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		87
12"	24"	36"	48"	60"	-	Custom Len.	
$54.56	$55.38	$56.22	$57.08	$57.91	-	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5252				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			88
12"	24"	36"	48"	60"	50CM	Custom Len.	
$286.46	$308.91	$331.37	$353.83	$376.28	$300.85	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0161				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			89
12"	18"	24"	36"	48"	60"	Custom Len.	
$534.98	$544.17	$553.36	$571.74	$590.12	$608.51	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0206				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			90
8"	12"	18"	24"	30"	36"	Custom Len.	
$489.78	$495.07	$503.06	$511.01	$518.99	$526.95	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0239				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.3" dia.			91
12"	18"	24"	36"	48"	60"	Custom Len.	
$601.05	$616.40	$631.73	$662.41	$693.11	$723.79	See Web	

Precision Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39481				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	92
6"	9"	12"	18"	24"	-	Custom Len.	
Call	$49.36	$51.45	$65.69	$63.94	-	See Web	

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39495				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	93
6"	9"	12"	18"	24"	-	Custom Len.	
$54.33	Call	$54.33	Call	Call	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39487				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	94
6"	9"	12"	18"	24"	-	Custom Len.	
Call	Call	$54.04	$65.69	$66.68	-	See Web	

Low Loss Test Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE346				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		95
12"	24"	36"	48"	60"	50CM	Custom Len.	
$259.48	$277.09	$294.69	$312.29	$329.89	$270.76	See Web	

Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE33867				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	96
12"	24"	36"	48"	60"	-	Custom Len.	
$69.00	$75.67	$82.35	$89.43	$96.24	-	See Web	

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1044				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			97
6"	12"	24"	36"	50CM	100CM	Custom Len.	
Call	$403.90	$378.31	Call	Call	Call	See Web	

TNC MALE TO TNC FEMALE

Precision Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39474				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	98
6"	9"	12"	18"	24"	-	Custom Len.	
$50.50	Call	Call	$57.81	$63.69	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39488				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	99
6"	9"	12"	18"	24"	-	Custom Len.	
$51.10	Call	$51.57	$55.37	$59.63	-	See Web	

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39496				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	1
6"	9"	12"	18"	24"	-	Custom Len.	
$51.37	$51.37	$51.37	$58.51	$59.19	-	See Web	

TNC MALE TO TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3W00780				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		2
12"	24"	36"	48"	60"	50CM	Custom Len.	
$42.70	$42.79	$42.86	$42.95	$43.04	$42.75	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0160				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			3
12"	18"	24"	36"	48"	60"	Custom Len.	
$504.81	$514.01	$523.19	$541.58	$559.96	$578.34	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0205				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			4
8"	12"	18"	24"	30"	36"	Custom Len.	
$485.51	$490.80	$498.79	$506.74	$514.72	$522.69	See Web	

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3W06580				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	5
12"	24"	36"	48"	60"	50CM	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

Standard Flexible Cable Assemblies

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1046				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			6
12"	24"	36"	50CM	100CM	-	Custom Len.	
$391.29	Call	$384.74	Call	Call	-	See Web	

TNC MALE TO REVERSE POLARITY TNC MALE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE37137				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	7
12"	24"	36"	48"	60"	-	Custom Len.	
$37.20	$37.93	$38.67	$43.55	$40.14	-	See Web	

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE35228				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	8
12"	24"	36"	48"	60"	72"	Custom Len.	
$44.65	$42.93	$43.79	$44.60	$45.39	$49.25	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE35230				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	9
12"	24"	36"	48"	60"	72"	Custom Len.	
$50.59	$56.43	$62.73	$69.04	$75.32	$81.63	See Web	

RG213/U Coax, 50 Ohm

Part No. PE35232				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	10
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.95	$74.78	$76.65	$78.49	$80.34	$82.11	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

RG214/U Coax, 50 Ohm

Part No. PE35234				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	11
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$89.97	$98.10	$114.46	$112.74	$120.73	$128.74	See Web	

RG223/U Coax, 50 Ohm

Part No. PE35236				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	12
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$47.46	$48.05	$51.26	$54.02	$57.17	$64.48	See Web	

RG316/U Coax, 50 Ohm

Part No. PE35238				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	13
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.00	$71.28	$74.61	$77.89	$81.19	$84.49	See Web	

REVERSE POLARITY TNC MALE TO BNC MALE

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE35229				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	14
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$45.68	$46.49	$47.31	$48.14	$48.96	$49.75	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE35231				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	15
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$44.65	$51.00	$56.83	$63.14	$69.43	$75.76	See Web	

RG213/U Coax, 50 Ohm

Part No. PE35233				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	16
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.29	$80.14	$82.00	$83.83	$85.70	$87.46	See Web	

RG214/U Coax, 50 Ohm

Part No. PE34520				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	17
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$83.83	$91.95	$100.08	$106.68	$114.68	$122.68	See Web	

RG223/U Coax, 50 Ohm

Part No. PE35235				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	18
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$38.39	$41.60	$44.85	$48.13	$51.32	$54.08	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3C3414				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	19
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft	160 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.13	$57.31	$60.47	$63.66	$66.84	$70.00	See Web	

TNC MALE RIGHT ANGLE TO N MALE

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C1041				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	20
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$247.33	$264.93	$267.51	$284.59	$301.67	$244.29	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0171				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	21
1 piece price shown. See web or call for volume pricing.				0.195" dia.			
12"	18"	24"	36"	48"	60"	Custom Len.	
$525.93	$535.12	$544.31	$562.70	$581.08	$599.46	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0216				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	22
1 piece price shown. See web or call for volume pricing.				0.16" dia.			
8"	12"	18"	24"	30"	36"	Custom Len.	
$475.62	$480.94	$488.90	$496.87	$504.85	$512.81	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0244				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	23
1 piece price shown. See web or call for volume pricing.				0.3" dia.			
12"	18"	24"	36"	48"	60"	Custom Len.	
$605.38	$620.72	$636.07	$666.74	$697.43	$728.11	See Web	

TNC MALE RIGHT ANGLE TO N MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0173				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	24
1 piece price shown. See web or call for volume pricing.				0.195" dia.			
12"	18"	24"	36"	48"	60"	Custom Len.	
$650.65	$659.83	$669.02	$687.41	$705.79	$724.17	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0218				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	25
1 piece price shown. See web or call for volume pricing.				0.16" dia.			
8"	12"	18"	24"	30"	36"	Custom Len.	
$581.93	$587.24	$595.22	$603.18	$611.16	$619.11	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0246				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	26
1 piece price shown. See web or call for volume pricing.				0.3" dia.			
12"	18"	24"	36"	48"	60"	Custom Len.	
$762.51	$777.86	$793.20	$823.88	$854.57	$885.25	See Web	

TNC MALE RIGHT ANGLE TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0172				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	27
1 piece price shown. See web or call for volume pricing.				0.195" dia.			
12"	18"	24"	36"	48"	60"	Custom Len.	
$620.47	$629.66	$638.86	$657.24	$675.62	$694.01	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0217				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	28
1 piece price shown. See web or call for volume pricing.				0.16" dia.			
8"	12"	18"	24"	30"	36"	Custom Len.	
$586.19	$591.52	$599.47	$607.45	$615.42	$623.38	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0245				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	29
1 piece price shown. See web or call for volume pricing.				0.3" dia.			
12"	18"	24"	36"	48"	60"	Custom Len.	
$687.42	$702.76	$718.10	$748.79	$779.48	$810.16	See Web	

TNC MALE RIGHT ANGLE TO TNC MALE

Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39473				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	30
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	
6"	9"	12"	18"	24"	-	Custom Len.	
Call	$51.73	Call	Call	Call	-	See Web	

Standard Semi-Rigid Cable Assemblies

PE-SR402AL Coax, 50 Ohm

Part No. PE3W07649				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	31
1 piece price shown. See web or call for volume pricing.						450 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$75.52	$86.38	$97.25	$106.60	$117.31	$82.48	See Web	

TNC MALE RIGHT ANGLE TO TNC MALE RIGHT ANGLE

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C1144				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	32
1 piece price shown. See web or call for volume pricing.				0.195" dia.	7.2 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$353.28	$370.88	$388.46	$406.08	$423.68	$364.55	See Web	

PE-P160LL Coax, 50 Ohm

Part No. PE3C5250				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	33
1 piece price shown. See web or call for volume pricing.				0.16" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$350.17	$372.63	$395.08	$417.54	$439.99	$364.55	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0170				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	34
1 piece price shown. See web or call for volume pricing.				0.195" dia.			
12"	18"	24"	36"	48"	60"	Custom Len.	
$650.65	$659.88	$669.02	$687.41	$705.79	$724.17	See Web	

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0215				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	35
1 piece price shown. See web or call for volume pricing.				0.16" dia.			
8"	12"	18"	24"	30"	36"	Custom Len.	
$581.93	$587.24	$595.22	$603.18	$611.16	$619.11	See Web	

PE-P300LL-27478 Coax, 50 Ohm

Part No. PE3M0243				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	36
1 piece price shown. See web or call for volume pricing.				0.3" dia.			
12"	18"	24"	36"	48"	60"	Custom Len.	
$757.49	$772.83	$788.17	$818.85	$849.53	$880.22	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

Precision Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE39494				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	450 W	37
6"	9"	12"	18"	24"	-	Custom Len.	
$56.76	$56.76	$56.76	Call	Call	-	See Web	

PE-SR405FL Coax, 50 Ohm

Part No. PE39472				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	38
6"	9"	12"	18"	24"	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39486				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	39
6"	9"	12"	18"	24"	-	Custom Len.	
$71.00	Call	$28.45	Call	Call	-	See Web	

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39480				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					11.88 dB/100ft	450 W	40
6"	9"	12"	18"	24"	-	Custom Len.	
$67.88	Call	Call	Call	$76.16	-	See Web	

Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE3194				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		41
12"	24"	36"	48"	-	-	Custom Len.	
$87.04	$93.73	$94.73	$101.04	-	-	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3W00037				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	42
12"	24"	36"	48"	60"	50CM	Custom Len.	
$102.78	$109.58	$117.85	$126.11	$134.37	$106.63	See Web	

PE-P141EAM Coax, 50 Ohm

Part No. PE3CA1045				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.163" dia.			43
12"	24"	36"	50CM	100CM	-	Custom Len.	
Call	Call	Call	Call	Call	-	See Web	

TNC MALE RIGHT ANGLE TO TNC FEMALE

Low Loss Flexible Cable Assemblies

LMR-240 Coax, 50 Ohm

Part No. PE3W06709				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.24" dia.	8 dB/100ft		44
12"	18"	24"	36"	48"	60"	Custom Len.	
$60.90	$59.07	$59.55	$60.47	$61.41	$62.35	See Web	

TNC MALE RIGHT ANGLE TO TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5254				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.16" dia.			45
12"	24"	36"	48"	60"	50CM	Custom Len.	
$314.95	$332.36	$354.47	$376.60	$398.70	$324.39	See Web	

TNC FEMALE TO SMA MALE

Standard Flexible Cable Assemblies

RG55B/U Coax, 53 Ohm

Part No. PE3W07646				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.		53 W	46
12"	24"	36"	48"	60"	50CM	Custom Len.	
$46.53	$49.61	$52.68	$55.26	$58.30	$48.50	See Web	

TNC FEMALE TO TNC MALE

Standard Formable Cable Assemblies

PE-SR402FL Coax, 50 Ohm

Part No. PE39482				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					12 dB/100ft	400 W	47
6"	9"	12"	18"	24"	-	Custom Len.	
Call	Call	$51.57	$62.40	$63.06	-	See Web	

TNC FEMALE TO TNC FEMALE

Standard Flexible Cable Assemblies

RG142B/U Coax, 50 Ohm

Part No. PE35480				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	48
12"	24"	36"	48"	60"	50CM	Custom Len.	
$53.12	$59.01	$65.38	$71.75	$78.12	$50.81	See Web	

TNC FEMALE TO REVERSE POLARITY TNC MALE

Standard Flexible Cable Assemblies

LMR-195 Coax, 50 Ohm

Part No. PE3C7597				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.8 dB/100ft		49
12"	24"	36"	48"	60"	50CM	Custom Len.	
$42.32	$43.04	$43.76	$44.49	$45.21	$42.79	See Web	

REVERSE POLARITY TNC FEMALE TO REVERSE POLARITY SMA MALE

Standard Flexible Cable Assemblies

RG55B/U Coax, 53 Ohm

Part No. PE3W07647				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	50
12"	24"	36"	48"	60"	50CM	Custom Len.	
$52.47	$55.04	$58.09	$61.14	$64.19	$54.44	See Web	

TNC FEMALE BULKHEAD TO MCX PLUG RIGHT ANGLE



SEE MOUNTING HOLE SECTION ON PAGE 409

Precision Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39477				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	51
6"	9"	12"	15"	18"	24"	Custom Len.	
$19.99	$23.01	$26.04	Call	$73.56	Call	See Web	

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39491				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	52
6"	9"	12"	18"	24"	-	Custom Len.	
$45.94	$47.40	$49.61	$50.08	$54.21	-	See Web	

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE33799				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W	53
12"	24"	36"	48"	60"	-	Custom Len.	
$72.12	$67.26	$67.71	$68.20	$68.68	-	See Web	

TNC FEMALE BULKHEAD TO MMCX PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Precision Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE39478				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	130 W	54
6"	9"	12"	18"	24"	-	Custom Len.	
$49.76	Call	$55.37	Call	Call	-	See Web	

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE39492				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	19.5 dB/100ft	130 W	55
6"	9"	12"	18"	24"	-	Custom Len.	
$47.58	$49.88	$52.17	$56.40	$61.10	-	See Web	

Standard Flexible Cable Assemblies

RG188A/U Coax, 50 Ohm

Part No. PE35635				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	56
12"	24"	36"	48"	60"	-	Custom Len.	
$79.32	$82.06	$84.80	$80.77	$83.21	-	See Web	

RG316/U Coax, 50 Ohm

Part No. PE3W04293				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.098" dia.	38 dB/100ft	160 W	57
12"	24"	36"	48"	60"	50CM	Custom Len.	
$92.61	$96.21	$99.83	$103.44	$107.04	$94.93	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

TNC FEMALE BULKHEAD TO N MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0167				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.		
12"	18"	24"	36"	48"	60"	Custom Len.
$495.75	$504.94	$514.13	$532.53	$550.90	$569.29	See Web

58

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0212				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
8"	12"	18"	24"	30"	36"	Custom Len.
$471.35	$476.67	$484.63	$492.60	$500.58	$508.55	See Web

59

TNC FEMALE BULKHEAD TO N MALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0169				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.		
12"	18"	24"	36"	48"	60"	Custom Len.
$620.47	$629.66	$638.86	$657.24	$675.62	$694.01	See Web

60

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0214				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
8"	12"	18"	24"	30"	36"	Custom Len.
$577.67	$582.96	$590.95	$598.92	$606.88	$614.85	See Web

61

TNC FEMALE BULKHEAD TO N FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0168				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.		
12"	18"	24"	36"	48"	60"	Custom Len.
$590.30	$599.49	$608.67	$627.07	$645.45	$663.83	See Web

62

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0213				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
8"	12"	18"	24"	30"	36"	Custom Len.
$581.93	$587.24	$595.22	$603.18	$611.16	$619.11	See Web

63

TNC FEMALE BULKHEAD TO SMA MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5260				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.	11 dB/100ft	560 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$251.25	$273.71	$296.15	$318.61	$341.07	$265.63	See Web

64

TNC FEMALE BULKHEAD TO SMA MALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FLJ Coax, 50 Ohm

Part No. PE3W03175				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.105" dia.	19.5 dB/100ft	121.5 W
12"	18"	24"	36"	48"	60"	Custom Len.
$78.25	$80.07	$84.80	$94.28	$103.75	$111.66	See Web

65

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE3W03417				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	32 dB/100ft	17 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$71.57	$72.18	$72.81	$73.42	$74.04	$71.95	See Web

66

RG178B/U Coax, 50 Ohm

Part No. PE3W05425				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.41 dB/100ft	55 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$76.67	$77.91	$79.15	$80.39	$81.64	$77.45	See Web

67

Standard Semi-Rigid Cable Assemblies

RG402/U Coax, 50 Ohm

Part No. PE3W10767				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					11.1 dB/100ft	450 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$135.71	$143.80	$151.90	$159.99	$168.08	$132.80	See Web

68

TNC FEMALE BULKHEAD TO SMC PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG174A/U Coax, 50 Ohm

Part No. PE36779				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	32 dB/100ft	16 W
12"	24"	36"	48"	60"	-	Custom Len.
$83.92	$76.76	$77.25	$77.73	$78.21	-	See Web

69

TNC FEMALE BULKHEAD TO SMP FEMALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE3W05541				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$123.14	$135.80	$148.47	$161.13	$173.79	$131.24	See Web

70

TNC FEMALE BULKHEAD TO SSMC PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG188A/U Coax, 50 Ohm

Part No. PE3W05752				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$112.70	$126.03	$128.92	$131.81	$134.71	$124.98	See Web

71

TNC FEMALE BULKHEAD TO TNC MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Flexible Cable Assemblies

PE-P160LL Coax, 50 Ohm

Part No. PE3C5253				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.	11 dB/100ft	560 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$251.25	$273.71	$296.15	$318.61	$341.07	$265.63	See Web

72

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE348				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$215.70	$233.29	$250.90	$268.50	$286.09	$226.98	See Web

73

TNC FEMALE BULKHEAD TO TNC MALE RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0166				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.		
12"	18"	24"	36"	48"	60"	Custom Len.
$620.47	$629.66	$638.86	$657.24	$675.62	$694.01	See Web

74

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0211				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.16" dia.		
8"	12"	18"	24"	30"	36"	Custom Len.
$577.67	$582.96	$590.95	$598.92	$606.88	$614.85	See Web

75

TNC FEMALE BULKHEAD TO TNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

PE-P142LL Coax, 50 Ohm

Part No. PE3C2180				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.195" dia.	10 dB/100ft	
12"	24"	36"	48"	60"	50CM	Custom Len.
$255.05	$272.66	$290.26	$307.86	$325.47	$266.33	See Web

76

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-P160LL Coax, 50 Ohm

Part No. PE3C5251				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	77
1 piece price shown. See web or call for volume pricing.				0.16" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$279.74	$302.20	$324.65	$347.11	$369.56	$294.13	See Web	

PE-P142LL-27478 Coax, 50 Ohm

Part No. PE3M0165					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	78
1 piece price shown. See web or call for volume pricing.					0.195" dia.			
12"	18"	24"	36"	48"	60"	Custom Len.		
$590.30	$599.49	$608.67	$627.07	$645.45	$663.83	See Web		

PE-P160LL-27478 Coax, 50 Ohm

Part No. PE3M0210				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	79
1 piece price shown. See web or call for volume pricing.				0.16" dia.			
8"	12"	18"	24"	30"	36"	Custom Len.	
$573.39	$578.70	$586.68	$594.65	$602.61	$610.58	See Web	

TNC FEMALE BULKHEAD TO UMCX PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38304				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	80
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	
3"	6"	9"	12"	18"	24"	Custom Len.	
$58.58	$60.46	$62.36	$64.24	$64.66	$68.70	See Web	

REVERSE POLARITY TNC FEMALE BULKHEAD TO MMCX PLUG

SEE MOUNTING HOLE SECTION ON PAGE 409

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W01379				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	81
1 piece price shown. See web or call for volume pricing.				0.11" dia.			
12"	24"	36"	48"	60"	50CM	Custom Len.	
$86.49	$87.29	$88.11	$88.92	$89.72	$87.01	See Web	

REVERSE POLARITY TNC FEMALE BULKHEAD TO REVERSE POLARITY SMA MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W07758				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	82
1 piece price shown. See web or call for volume pricing.				0.11" dia.	24 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.	
$111.36	$112.17	$112.97	$113.77	$114.58	$111.87	See Web	

REVERSE POLARITY TNC FEMALE BULKHEAD TO SSMC PLUG RIGHT ANGLE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG188A/U Coax, 50 Ohm

Part No. PE3W05762				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	83
1 piece price shown. See web or call for volume pricing.				0.11" dia.	26 dB/100ft	160 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$103.09	$106.02	$107.44	$110.34	$113.23	$104.96	See Web	

REVERSE POLARITY TNC FEMALE BULKHEAD TO REVERSE POLARITY TNC MALE

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Formable Cable Assemblies

PE-SR402FLJ Coax, 50 Ohm

Part No. PE3W05610				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	84
1 piece price shown. See web or call for volume pricing.				0.161" dia.	11.89 dB/100ft	303.4 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$90.60	$100.37	$108.60	$118.23	$127.87	$96.85	See Web	

REVERSE POLARITY TNC FEMALE BULKHEAD TO UMCX PLUG

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38303				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	85
1 piece price shown. See web or call for volume pricing.				0.072" dia.			
3"	6"	9"	12"	18"	24"	Custom Len.	
$58.90	$58.90	$58.90	$61.25	$62.95	$66.99	See Web	

UHF MALE TO BNC MALE

Low Loss Flexible Cable Assemblies

PE-C195 Coax, 50 Ohm

Part No. PE38674				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	86
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	
12"	24"	36"	48"	60"	-	Custom Len.	
$29.04	$29.84	$30.63	$33.44	$32.74	-	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE34581				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	87
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.18	$73.21	$81.15	$79.20	$82.18	$85.22	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3057				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	88
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$40.43	$41.34	$42.23	$43.19	$44.11	$45.03	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE3898				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	89
1 piece price shown. See web or call for volume pricing.				0.195" dia.	13 dB/100ft	650 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$39.31	$45.67	$52.03	$57.85	$64.16	$70.46	See Web	

RG213/U Coax, 50 Ohm

Part No. PE34583				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	90
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$73.12	$74.96	$76.77	$78.61	$80.43	$82.27	See Web	

RG214/U Coax, 50 Ohm

Part No. PE33438				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	91
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.55	$80.67	$88.78	$103.06	$105.02	$111.55	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3803				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	92
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$36.21	$39.43	$42.66	$45.87	$49.09	$52.30	See Web	

RG225/U Coax, 50 Ohm

Part No. PE34589				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	93
1 piece price shown. See web or call for volume pricing.				0.43" dia.		1,700 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$105.86	$132.00	$167.32	$202.65	$237.98	$273.29	See Web	

RG393/U Coax, 50 Ohm

Part No. PE34585				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	94
1 piece price shown. See web or call for volume pricing.				0.39" dia.	8.8 dB/100ft	1,700 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$84.10	$101.11	$116.48	$133.25	$150.02	$166.77	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3231				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	95
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	600 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$48.29	$58.85	$66.99	$70.83	$78.50	$86.17	See Web	

PE-B400 Coax, 50 Ohm

Part No. PE34579				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	96
1 piece price shown. See web or call for volume pricing.				0.403" dia.	6 dB/100ft	190 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$68.39	$70.18	$71.94	$73.75	$75.53	$77.29	See Web	

RG55B/U Coax, 53 Ohm

Part No. PE34591				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	97
1 piece price shown. See web or call for volume pricing.				0.202" dia.	16.5 dB/100ft	53 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$35.28	$37.76	$40.25	$42.74	$45.23	$47.70	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3543				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	98
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$31.87	$32.87	$33.86	$34.85	$35.88	$36.86	See Web	

RG62A/U Coax, 93 Ohm

Part No. PE34587				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	99
1 piece price shown. See web or call for volume pricing.				0.242" dia.	13 dB/100ft	77 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$34.92	$36.43	$37.95	$42.24	$41.00	$42.51	See Web	

UHF MALE TO UHF MALE

Low Loss Flexible Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

PE-C195 Coax, 50 Ohm

Part No. PE38632				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	11.3 dB/100ft	150 W	1
12"	24"	36"	48"	60"	-	Custom Len.	
$28.01	$28.74	$29.66	$31.12	$32.65	-	See Web	

PE-C400 Coax, 50 Ohm

Part No. PE35021				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.4" dia.	4.1 dB/100ft	550 W	2
12"	24"	36"	48"	60"	-	Custom Len.	
$55.37	$57.50	$62.77	$68.07	$73.35	-	See Web	

Standard Flexible Cable Assemblies

RG8A/U Coax, 50 Ohm

Part No. PE3623				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	3
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.54	$68.43	$71.54	$74.67	$77.76	$80.89	See Web	

RG58C/U Coax, 50 Ohm

Part No. PE3015				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	4
12"	24"	36"	48"	60"	72"	Custom Len.	
$41.19	$42.10	$42.99	$43.96	$44.88	$45.80	See Web	

RG142B/U Coax, 50 Ohm

Part No. PE33053				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	12.9 dB/100ft		5
12"	24"	36"	48"	60"	-	Custom Len.	
$41.20	$47.94	$54.19	$57.42	$63.74	-	See Web	

RG213/U Coax, 50 Ohm

Part No. PE3635				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.	8 dB/100ft	190 W	6
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.95	$64.76	$66.58	$68.41	$70.24	$72.06	See Web	

RG214/U Coax, 50 Ohm

Part No. PE3796				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.425" dia.	7.32 dB/100ft	190 W	7
12"	24"	48"	60"	72"	-	Custom Len.	
$75.11	$77.61	$93.72	$101.77	$117.07	-	See Web	

RG223/U Coax, 50 Ohm

Part No. PE3845				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.21" dia.	13.4 dB/100ft	53 W	8
12"	24"	36"	48"	60"	72"	Custom Len.	
$34.99	$38.21	$41.44	$44.66	$47.87	$51.08	See Web	

RG393/U Coax, 50 Ohm

Part No. PE33267				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.39" dia.	7.5 dB/100ft	1,700 W	9
12"	24"	36"	48"	60"	72"	Custom Len.	
$78.87	$91.41	$113.34	$123.67	$140.45	$157.20	See Web	

RG400/U Coax, 50 Ohm

Part No. PE3743				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	14.7 dB/100ft	650 W	10
12"	24"	36"	48"	60"	-	Custom Len.	
$46.20	$53.94	$61.12	$68.77	$76.44	-	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3580				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	11
12"	24"	36"	48"	60"	72"	Custom Len.	
$31.21	$32.20	$33.20	$37.23	$35.19	$36.20	See Web	

HMCX32 1.2 PLUG TO HMCX32 1.2 PLUG

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1058				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			12
6"	9"	12"	2CM	-	-	Custom Len.	
$11.46	$12.32	$13.20	Call	-	-	See Web	

UMCX PLUG RIGHT ANGLE TO MCX PLUG

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38890				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	13
3"	6"	9"	12"	18"	24"	Custom Len.	
$68.17	$69.85	$68.17	$73.62	$72.20	$76.25	See Web	

UMCX PLUG RIGHT ANGLE TO MCX PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38502				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	14
3"	6"	9"	12"	18"	24"	Custom Len.	
$63.00	$64.26	$63.00	$63.00	$67.04	$71.09	See Web	

UMCX PLUG RIGHT ANGLE TO MCX JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38889				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	15
3"	6"	9"	12"	18"	24"	Custom Len.	
$80.19	$80.19	$80.19	$86.61	$84.24	$88.28	See Web	

PE-113mm Coax, 50 Ohm

Part No. PE38298				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.045" dia.			16
6"	12"	18"	-	-	-	Custom Len.	
$26.67	$25.97	$24.55	-	-	-	See Web	

UMCX PLUG RIGHT ANGLE TO REVERSE POLARITY MCX JACK BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38302				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	17
3"	6"	9"	12"	18"	24"	Custom Len.	
$82.15	$82.15	$82.15	$82.15	$86.21	$90.25	See Web	

UMCX PLUG RIGHT ANGLE TO MMCX PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE39078				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	18
3"	6"	9"	12"	18"	24"	Custom Len.	
$69.11	$70.99	$72.88	$74.76	$78.64	$82.54	See Web	

UMCX PLUG RIGHT ANGLE TO SSMB PLUG

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38930				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.	44.4 dB/100ft	78 W	19
3"	6"	9"	12"	18"	24"	Custom Len.	
$107.73	$107.73	$107.73	$107.73	$112.53	$126.73	See Web	

UMCX 2.1 PLUG TO UMCX 2.1 PLUG

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1056				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			20
6"	9"	12"	5CM	8CM	9CM	Custom Len.	
$9.26	$11.27	$11.94	Call	Call	Call	See Web	

UMCX 2.5 PLUG TO UMCX 2.5 PLUG

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE3CA1054				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.07" dia.			21
6"	9"	12"	-	-	-	Custom Len.	
$11.70	$13.36	$14.70	-	-	-	See Web	

RG178-DS Coax, 50 Ohm

Part No. PE3CA1055				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.086" dia.			22
6"	9"	12"	1000CM	-	-	Custom Len.	
$12.22	$14.70	$18.90	Call	-	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

PE-81mm Coax, 50 Ohm

Part No. PE3CA1051				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			23
3"	6"	9"	12"	15"	36CM	Custom Len.	
Call	$8.91	$9.69	$15.83	Call	Call	See Web	

PE-113mm Coax, 50 Ohm

Part No. PE3CA1052				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.044" dia.			24
1"	2"	3"	6"	9"	12"	Custom Len.	
Call	Call	Call	$10.20	$10.07	$11.94	See Web	

PE-137mm Coax, 50 Ohm

Part No. PE3CA1053				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.053" dia.			25
6"	9"	12"	-	-	-	Custom Len.	
$10.64	$11.46	$12.46	-	-	-	See Web	

WMCX 1.6 PLUG TO WMCX 1.6 PLUG

Standard Flexible Cable Assemblies

PE-81mm Coax, 50 Ohm

Part No. PE3CA1057				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.032" dia.			26
6"	9"	12"	-	-	-	Custom Len.	
$9.84	$10.63	$12.59	-	-	-	See Web	

NEX10 MALE TO NEX10 MALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7849				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		27
12"	24"	36"	48"	60"	50CM	Custom Len.	
$69.11	$72.84	$76.57	$80.29	$84.02	$71.50	See Web	

SPP-250-LLPL Coax, 50 Ohm

Part No. PE3C6253				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.28" dia.	5.5 dB/100ft	650 W	28
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.74	$80.88	$87.01	$93.14	$99.28	$78.66	See Web	

NEX10 MALE TO NEX10 MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7850				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		29
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.61	$78.34	$82.06	$85.79	$89.52	$77.00	See Web	

NEX10 MALE TO NEX10 FEMALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7851				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		30
12"	24"	36"	48"	60"	50CM	Custom Len.	
$65.81	$69.54	$73.26	$77.00	$80.72	$68.20	See Web	

NEX10 MALE TO NEX10 FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7852				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		31
12"	24"	36"	48"	60"	50CM	Custom Len.	
$68.56	$72.29	$76.02	$79.74	$83.47	$70.95	See Web	

NEX10 MALE RIGHT ANGLE TO NEX10 MALE RIGHT ANGLE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7853				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		32
12"	24"	36"	48"	60"	50CM	Custom Len.	
$80.11	$83.83	$87.56	$91.29	$95.01	$82.50	See Web	

NEX10 MALE RIGHT ANGLE TO NEX10 FEMALE

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7854				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		33
12"	24"	36"	48"	60"	50CM	Custom Len.	
$71.31	$75.03	$78.76	$82.50	$86.22	$73.69	See Web	

NEX10 MALE RIGHT ANGLE TO NEX10 FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Low PIM Corrugated Cable Assemblies

PE-1/4SFHC Coax, 50 Ohm

Part No. PE3C7855				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.303" dia.	5.85 dB/100ft		34
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.06	$77.79	$81.51	$85.24	$88.96	$76.45	See Web	

1.85MM NMD FEMALE TO 1.85MM MALE

Precision Flexible Cable Assemblies

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC0960				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.27" dia.			35
24"	48"	-	-	-	-	Custom Len.	
$3,927.29	$4,057.39	-	-	-	-	See Web	

1.85MM NMD FEMALE TO 1.85MM FEMALE

Precision Flexible Cable Assemblies

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC0970				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.27" dia.			36
24"	48"	-	-	-	-	Custom Len.	
$3,927.29	$4,057.39	-	-	-	-	See Web	

2.4MM NMD FEMALE TO 2.4MM MALE

Precision Flexible Cable Assemblies

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC0660				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.27" dia.			37
24"	48"	-	-	-	-	Custom Len.	
$3,566.80	$3,699.61	-	-	-	-	See Web	

2.4MM NMD FEMALE TO 2.4MM FEMALE

Precision Flexible Cable Assemblies

PE-VNA-HF Coax, 50 Ohm

Part No. PE3TC0670				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.27" dia.			38
24"	48"	-	-	-	-	Custom Len.	
$3,566.80	$3,699.61	-	-	-	-	See Web	

2.92MM NMD FEMALE TO 2.92MM MALE

Standard Flexible Cable Assemblies

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA4007				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			39
24"	36"	48"	-	-	-	Custom Len.	
$2,456.91	$2,573.07	$2,685.71	-	-	-	See Web	

2.92MM NMD FEMALE TO 2.92MM FEMALE

Standard Flexible Cable Assemblies

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA4008				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.43" dia.			40
24"	36"	48"	-	-	-	Custom Len.	
$2,527.30	$2,643.47	$2,752.60	-	-	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

3.5MM FEMALE TO 3.5MM NMD FEMALE

Standard Flexible Cable Assemblies

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA2610				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	41
1 piece price shown. See web or call for volume pricing.				0.43" dia.			
24"	36"	48"	-	-	-	Custom Len.	
$1,876.08	$1,985.20	$2,094.34	-	-	-	See Web	

3.5MM NMD FEMALE TO 3.5MM MALE

Standard Flexible Cable Assemblies

PE-VNA-R Coax, 50 Ohm

Part No. PE3VNA2607				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	42
1 piece price shown. See web or call for volume pricing.				0.43" dia.			
24"	36"	48"	-	-	-	Custom Len.	
$1,840.88	$1,950.00	$2,059.13	-	-	-	See Web	

D-SUBMINIATURE RECEPTACLE TO BNC MALE

Low Loss Flexible Cable Assemblies

LMR-100A-PVC Coax, 50 Ohm

Part No. PE3W01818					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	43
1 piece price shown. See web or call for volume pricing.					0.11" dia.	24 dB/100ft		
12"	24"	36"	48"	60"	50CM	Custom Len.		
Call	Call	Call	Call	Call	Call	See Web		

MCX PLUG TO 75 OHM BNC MALE

Standard Flexible Cable Assemblies

RG187A/U Coax, 75 Ohm

Part No. PE3C5491					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	44
1 piece price shown. See web or call for volume pricing.					0.102" dia.	25 dB/100ft	200 W	
12"	24"	36"	48"	60"	50CM	Custom Len.		
$52.00	$53.18	$56.76	$60.84	$64.92	$51.69	See Web		

2.92MM FEMALE BULKHEAD TO STRAIGHT CUT LEAD SEXLESS

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Semi-Rigid Cable Assemblies

RG405/U Coax, 50 Ohm

Part No. PE3C7619					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	45
1 piece price shown. See web or call for volume pricing.						22 dB/100ft	130 W	
12"	24"	36"	48"	60"	50CM	Custom Len.		
$202.37	$210.18	$218.00	$225.82	$233.63	$207.38	See Web		

3.5MM FEMALE TO STRAIGHT CUT LEAD SEXLESS

Standard Semi-Rigid Cable Assemblies

RG402/U Coax, 50 Ohm

Part No. PE3C7590					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	46
1 piece price shown. See web or call for volume pricing.						11.1 dB/100ft	450 W	
12"	24"	36"	48"	60"	50CM	Custom Len.		
$133.06	$141.30	$149.54	$157.77	$166.02	$138.34	See Web		

BNC MALE TO NMO MOUNT SEXLESS

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37844				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	47
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
60"	120"	180"	-	-	-	Custom Len.	
$47.11	$55.14	$54.77	-	-	-	See Web	

BNC MALE TO STRAIGHT CUT LEAD SEXLESS

Standard Flexible Cable Assemblies

RG188A/U Coax, 50 Ohm

Part No. PE3C3583					Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	48
1 piece price shown. See web or call for volume pricing.					0.11" dia.	26 dB/100ft	160 W	
12"	50CM	24"	36"	100CM	48"	Custom Len.		
$26.40	$27.42	$28.39	$31.07	$31.82	$33.75	See Web		

BNC FEMALE TO NMO MOUNT SEXLESS

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37845				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	49
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
60"	120"	180"	-	-	-	Custom Len.	
$45.92	$49.99	$54.04	-	-	-	See Web	

FME PLUG TO NMO MOUNT SEXLESS

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37842				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	50
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
60"	120"	180"	-	-	-	Custom Len.	
$49.32	$53.38	$56.91	-	-	-	See Web	

FME JACK TO NMO MOUNT SEXLESS

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37843				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	51
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
60"	120"	180"	-	-	-	Custom Len.	
$45.25	$49.32	$53.38	-	-	-	See Web	

MINI UHF MALE TO NMO MOUNT SEXLESS

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37846				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	52
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
60"	120"	180"	-	-	-	Custom Len.	
$45.84	$49.92	$54.00	-	-	-	See Web	

MINI UHF FEMALE TO NMO MOUNT SEXLESS

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37847				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	53
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
60"	120"	180"	-	-	-	Custom Len.	
$49.71	$53.77	$57.31	-	-	-	See Web	

N MALE TO NMO MOUNT SEXLESS

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37850				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	54
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
60"	120"	180"	-	-	-	Custom Len.	
$57.61	$62.16	$66.73	-	-	-	See Web	

N FEMALE TO NMO MOUNT SEXLESS

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37851				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	55
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
60"	120"	180"	-	-	-	Custom Len.	
$53.25	$56.77	$66.26	-	-	-	See Web	

SMA MALE TO NMO MOUNT SEXLESS

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37840				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	56
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	
60"	120"	180"	-	-	-	Custom Len.	
$56.19	$55.94	$65.30	-	-	-	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

SMA MALE TO STRAIGHT CUT LEAD SEXLESS

Flexible Cable Assemblies

RG188-DS Coax, 50 Ohm

Part No. PE3C6848				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.118" dia.	30 dB/100ft	160 W	57
12"	24"	36"	48"	60"	50CM	Custom Len.	
$27.68	$31.05	$33.10	$37.20	$41.29	$27.52	See Web	

SMA FEMALE TO NMO MOUNT SEXLESS

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37841				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	58
60"	120"	180"	-	-	-	Custom Len.	
$66.04	$65.05	$69.10	-	-	-	See Web	

SMA FEMALE TO TRIMMED LEAD SEXLESS



Standard Semi-Rigid Cable Assemblies

PE-020SR Coax, 50 Ohm

Part No. PE3CA1104				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.02" dia.			59
-	3"	6"	9"	12"	15CM	Custom Len.	
-	$104.73	$122.24	$141.22	$158.09	Call	See Web	

PE-034SR Coax, 50 Ohm

Part No. PE3CA1105				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.034" dia.			60
3"	15CM	6"	9"	12"	-	Custom Len.	
$39.51	Call	$47.19	$54.03	$60.72	-	See Web	

PE-SR047TN Coax, 50 Ohm

Part No. PE3CA1106				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.			61
3"	6"	9"	12"	-	-	Custom Len.	
$43.95	$46.98	$52.38	$57.66	-	-	See Web	

SMA FEMALE TO STRAIGHT CUT LEAD SEXLESS

Standard Semi-Rigid Cable Assemblies

PE-020SR Coax, 50 Ohm

Part No. PE3CA1107				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.02" dia.			62
3"	6"	9"	12"	-	-	Custom Len.	
$67.10	$88.37	$107.53	$127.92	-	-	See Web	

PE-034SR Coax, 50 Ohm

Part No. PE3CA1102				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.034" dia.			63
3"	6"	9"	12"	-	-	Custom Len.	
$34.79	$40.61	$46.47	$52.35	-	-	See Web	

PE-047SR Coax, 50 Ohm

Part No. PE3CA1103				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.047" dia.			64
3"	6"	9"	12"	-	-	Custom Len.	
$34.58	$40.42	$46.26	$52.15	-	-	See Web	

SSMA MALE TO TRIMMED LEAD SEXLESS

Formable Cable Assemblies

PE-SR405FL Coax, 50 Ohm

Part No. PE3C6783				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.					22.5 dB/100ft	105 W	65
12"	24"	36"	48"	60"	50CM	Custom Len.	
$78.14	$90.98	$97.41	$108.72	$121.38	$79.95	See Web	

SSMB PLUG RIGHT ANGLE TO STRAIGHT CUT LEAD SEXLESS

Standard Flexible Cable Assemblies

RG316/U Coax, 50 Ohm

Part No. PE3C7425				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	38 dB/100ft		66
12"	50CM	24"	36"	100CM	48"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

TNC FEMALE TO NMO MOUNT SEXLESS

Standard Flexible Cable Assemblies

RG58C/U Coax, 50 Ohm

Part No. PE37849				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.	20 dB/100ft	44 W	67
60"	120"	180"	-	-	-	Custom Len.	
$54.69	$58.74	$62.77	-	-	-	See Web	

UMCX PLUG RIGHT ANGLE TO STRAIGHT CUT LEAD SEXLESS

Standard Flexible Cable Assemblies

RG178B/U Coax, 50 Ohm

Part No. PE38296				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.072" dia.			68
3"	6"	9"	12"	18"	24"	Custom Len.	
$46.71	$30.80	$46.71	$30.80	$34.87	$41.10	See Web	

75 OHM 1.6/5.6 PLUG TO 75 OHM 1.6/5.6 PLUG

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE36109				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	69
12"	24"	36"	48"	60"	72"	Custom Len.	
$45.05	$46.04	$47.05	$48.05	$49.05	$50.05	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE36111				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	70
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.53	$57.17	$59.82	$62.40	$65.04	$67.61	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE36113				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	71
12"	24"	36"	48"	60"	72"	Custom Len.	
$55.61	$65.36	$62.77	$66.42	$70.04	$73.68	See Web	

75 OHM 1.6/5.6 PLUG TO 75 OHM 1.6/5.6 PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

RG179B/U Coax, 75 Ohm

Part No. PE36117				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	72
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.83	$67.40	$70.04	$72.68	$75.26	$77.89	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE36119				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	73
12"	24"	36"	48"	60"	72"	Custom Len.	
$65.82	$69.44	$73.07	$76.65	$80.28	$83.89	See Web	

75 OHM 1.6/5.6 PLUG TO 75 OHM BNC MALE

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE36127				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	74
12"	24"	36"	48"	60"	72"	Custom Len.	
$44.34	$49.04	$46.47	$47.55	$48.59	$49.67	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE36129				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	75
12"	24"	36"	48"	60"	72"	Custom Len.	
$52.11	$54.20	$56.86	$59.48	$62.05	$64.70	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE36131				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	76
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.11	$56.26	$59.88	$63.45	$67.06	$70.69	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

75 OHM 1.6/5.6 PLUG RIGHT ANGLE TO 75 OHM 1.6/5.6 PLUG RIGHT ANGLE



Standard Flexible Cable Assemblies

RG179B/U Coax, 75 Ohm — 77

Part No. PE36123				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W
12"	24"	36"	48"	60"	72"	Custom Len.
$75.04	$77.69	$80.28	$82.91	$85.54	$88.12	See Web

RG187A/U Coax, 75 Ohm — 78

Part No. PE36125				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W
12"	24"	36"	48"	60"	72"	Custom Len.
$76.05	$79.69	$83.29	$86.94	$90.57	$94.13	See Web

75 OHM BNC MALE TO 75 OHM BNC MALE

Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm — 79

Part No. PE33197				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	100 W
12"	24"	36"	48"	60"	72"	Custom Len.
$48.77	$50.31	$55.99	$55.74	$63.95	$67.88	See Web

RG6-CATV Coax, 75 Ohm — 80

Part No. PE37808				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.275" dia.	6.55 dB/100ft	6.5 W
12"	24"	36"	48"	60"	-	Custom Len.
$63.54	$64.85	$66.18	$67.57	$63.39	-	See Web

RG11A/U Coax, 75 Ohm — 81

Part No. PE33399				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W
12"	24"	36"	48"	60"	72"	Custom Len.
$74.44	$76.33	$78.22	$80.11	$82.00	$83.88	See Web

RG59B/U Coax, 75 Ohm — 82

Part No. PE33188				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$44.11	$45.26	$46.42	$47.64	$48.82	$49.98	See Web

RG179B/U Coax, 75 Ohm — 83

Part No. PE33401				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W
12"	24"	36"	48"	60"	72"	Custom Len.
$54.66	$57.47	$60.28	$63.26	$66.13	$69.00	See Web

PE-B150 Coax, 75 Ohm — 84

Part No. PE33405				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.15" dia.	20 dB/100ft	25 W
12"	24"	36"	48"	60"	72"	Custom Len.
$62.69	$68.73	$69.73	$65.30	$66.18	$67.04	See Web

PE-B159-BL Coax, 75 Ohm — 85

Part No. PE38130				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.159" dia.	10.5 dB/100ft	
12"	24"	36"	48"	60"	72"	Custom Len.
$48.87	$49.57	$50.27	$50.98	$51.68	$52.88	See Web

75 OHM BNC MALE TO 75 OHM BNC MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm — 86

Part No. PE33407				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	125 W
12"	24"	36"	48"	60"	72"	Custom Len.
$74.23	$77.20	$80.14	$83.09	$86.02	$88.95	See Web

RG59B/U Coax, 75 Ohm — 87

Part No. PE33196				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$60.75	$61.82	$67.90	$63.92	$64.99	$66.03	See Web

88

Part No. PE3W00288				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.		77 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$78.10	$79.20	$80.31	$81.43	$82.54	$78.81	See Web

RG179B/U Coax, 75 Ohm — 89

Part No. PE33412				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W
12"	24"	36"	48"	60"	72"	Custom Len.
$67.27	$70.08	$69.88	$75.86	$75.05	$77.68	See Web

RG187A/U Coax, 75 Ohm — 90

Part No. PE33414				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W
12"	24"	36"	48"	60"	72"	Custom Len.
$68.49	$72.68	$76.88	$75.83	$79.57	$83.29	See Web

75 OHM BNC MALE TO 75 OHM BNC FEMALE

Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm — 91

Part No. PE33437				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	125 W
12"	24"	36"	48"	60"	72"	Custom Len.
$86.50	$89.44	$92.38	$95.33	$107.34	$101.22	See Web

RG11A/U Coax, 75 Ohm — 92

Part No. PE33439				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W
12"	24"	36"	48"	60"	72"	Custom Len.
Call	Call	Call	Call	Call	Call	See Web

RG179B/U Coax, 75 Ohm — 93

Part No. PE33443				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W
12"	24"	36"	48"	60"	72"	Custom Len.
$58.18	$64.48	$63.37	$65.97	$68.57	$75.99	See Web

RG187A/U Coax, 75 Ohm — 94

Part No. PE33445				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W
12"	24"	36"	48"	60"	72"	Custom Len.
$59.26	$63.00	$66.74	$70.49	$74.21	$77.96	See Web

75 OHM BNC MALE TO 75 OHM BNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm — 95

Part No. PE33417				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	125 W
12"	24"	36"	48"	60"	72"	Custom Len.
$93.75	$96.70	$99.65	$102.57	$105.52	$106.95	See Web

RG59B/U Coax, 75 Ohm — 96

Part No. PE33179				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$65.67	$66.80	$61.81	$62.86	$63.92	$64.98	See Web

RG179B/U Coax, 75 Ohm — 97

Part No. PE33421				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W
12"	24"	36"	48"	60"	72"	Custom Len.
$67.93	$70.73	$68.10	$70.69	$73.28	$75.90	See Web

PE-B150 Coax, 75 Ohm — 98

Part No. PE33425				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.15" dia.	20 dB/100ft	25 W
12"	24"	36"	48"	60"	72"	Custom Len.
$75.89	$76.75	$77.62	$78.49	$79.35	$80.25	See Web

PE-B159-BL Coax, 75 Ohm — 99

Part No. PE38132				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.159" dia.	10.5 dB/100ft	
12"	24"	36"	48"	60"	72"	Custom Len.
$54.35	$55.99	$57.64	$59.30	$61.00	$62.67	See Web

75 OHM BNC MALE RIGHT ANGLE TO 75 OHM BNC MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm — 1

Part No. PE33426				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	125 W
12"	24"	36"	48"	60"	72"	Custom Len.
$93.64	$96.58	$99.52	$102.45	$105.39	$106.85	See Web

RG59B/U Coax, 75 Ohm — 2

Part No. PE33430				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$81.84	$82.89	$90.68	$85.00	$86.06	$87.12	See Web

RG179B/U Coax, 75 Ohm — 3

Part No. PE33432				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	29.15 dB/100ft	
12"	24"	36"	48"	60"	72"	Custom Len.
$75.44	$78.02	$80.63	$83.23	$85.83	$88.42	See Web

See Our Website For Current Pricing & Real-Time Stock Availability!

RG187A/U Coax, 75 Ohm

Part No. PE33434				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	4
12"	24"	36"	48"	60"	72"	Custom Len.	
$76.49	$80.24	$89.47	$87.71	$91.45	$95.19	See Web	

75 OHM BNC FEMALE TO 75 OHM BNC FEMALE

Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm

Part No. PE33448				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	125 W	5
12"	24"	36"	48"	60"	72"	Custom Len.	
$109.93	$111.94	$113.91	$115.91	$117.86	$119.89	See Web	

RG11A/U Coax, 75 Ohm

Part No. PE33450				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W	6
12"	24"	36"	48"	60"	72"	Custom Len.	
$98.94	$100.73	$102.56	$104.41	$106.20	$106.55	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE33451				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	7
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.04	$61.65	$64.30	$66.87	$69.51	$76.91	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE33456				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	8
12"	24"	36"	48"	60"	72"	Custom Len.	
$60.09	$63.64	$67.29	$70.91	$74.51	$78.15	See Web	

75 OHM BNC FEMALE BULKHEAD TO 75 OHM BNC FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Flexible Cable Assemblies

RG187A/U Coax, 75 Ohm

Part No. PE3W07034				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.	25 dB/100ft	200 W	9
12"	24"	36"	48"	60"	50CM	Custom Len.	
$73.47	$78.03	$80.27	$84.89	$89.47	$74.10	See Web	

Standard Flexible Cable Assemblies

RG62A/U Coax, 93 Ohm

Part No. PE3W06444				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.239" dia.	8.7 dB/100ft	77 W	10
12"	24"	36"	48"	60"	50CM	Custom Len.	
$74.04	$76.57	$79.11	$81.66	$84.20	$75.65	See Web	

75 OHM F MALE TO 75 OHM BNC MALE

Standard Flexible Cable Assemblies

RG6-CATV Coax, 75 Ohm

Part No. PE36145				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.275" dia.	6.55 dB/100ft	6.5 W	11
12"	24"	36"	48"	60"	72"	Custom Len.	
$36.42	$37.75	$36.66	$40.49	$41.83	$40.12	See Web	

RG11A/U Coax, 75 Ohm

Part No. PE36147				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W	12
12"	24"	36"	48"	60"	72"	Custom Len.	
$58.61	$60.52	$62.40	$64.28	$66.18	$68.06	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE36149				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	13
12"	24"	36"	48"	60"	72"	Custom Len.	
$32.01	$30.70	$34.31	$35.53	$36.71	$34.96	See Web	

RG59-WHITE Coax, 75 Ohm

Part No. PE36151				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	8.09 dB/100ft	77 W	14
12"	24"	36"	48"	60"	72"	Custom Len.	
$29.78	$31.96	$34.13	$36.31	$38.49	$40.67	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE36153				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	29.15 dB/100ft		15
12"	24"	36"	48"	60"	72"	Custom Len.	
$43.80	$46.65	$49.48	$48.44	$51.06	$53.69	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE36155				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	16
12"	24"	36"	48"	60"	72"	Custom Len.	
$47.20	$47.49	$51.26	$54.53	$58.27	$62.01	See Web	

75 OHM F MALE TO 75 OHM F MALE

Low Loss Flexible Cable Assemblies

PE-SF200LL75 Coax, 75 Ohm

Part No. PE3TC1202				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			17
24"	36"	48"	72"	100CM	200CM	Custom Len.	
$94.44	$106.82	$117.55	$141.95	$108.77	$148.82	See Web	

Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm

Part No. PE37163				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	125 W	18
12"	24"	36"	48"	60"	-	Custom Len.	
$18.78	$23.88	$27.86	$31.21	$35.16	-	See Web	

RG6-CATV Coax, 75 Ohm

Part No. PE36132				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.275" dia.	6.55 dB/100ft	6.5 W	19
12"	24"	36"	48"	60"	72"	Custom Len.	
$21.53	$22.90	$24.28	$25.72	$27.10	$27.73	See Web	

RG11A/U Coax, 75 Ohm

Part No. PE36135				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W	20
12"	24"	36"	48"	60"	72"	Custom Len.	
$43.99	$45.89	$51.20	$49.70	$51.62	$53.51	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE36141				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	21
12"	24"	36"	48"	60"	72"	Custom Len.	
$18.70	$19.87	$21.06	$22.32	$22.01	$23.11	See Web	

RG59-WHITE Coax, 75 Ohm

Part No. PE36143				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	8.09 dB/100ft	77 W	22
12"	24"	36"	48"	60"	72"	Custom Len.	
$18.52	$20.77	$23.02	$25.27	$27.55	$28.93	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE36137				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	23
12"	24"	36"	48"	60"	72"	Custom Len.	
$30.08	$30.95	$35.75	$36.27	$38.86	$41.52	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE36139				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	24
12"	24"	36"	48"	60"	72"	Custom Len.	
$31.05	$31.77	$35.30	$38.73	$42.28	$45.80	See Web	

PE-B159-BL Coax, 75 Ohm

Part No. PE38136				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.159" dia.	10.5 dB/100ft		25
12"	24"	36"	48"	60"	72"	Custom Len.	
$24.94	$27.33	$30.14	$33.06	$36.00	$38.99	See Web	

75 OHM F MALE TO 75 OHM F MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE38343				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	26
12"	24"	36"	48"	60"	-	Custom Len.	
$24.13	$27.72	$26.31	$27.41	$27.72	-	See Web	

PE-B159-BL Coax, 75 Ohm

Part No. PE38137				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.159" dia.	10.5 dB/100ft		27
12"	24"	36"	48"	60"	72"	Custom Len.	
$37.81	$39.44	$41.11	$42.80	$44.46	$46.13	See Web	

75 OHM F MALE TO 75 OHM F FEMALE

Low Loss Flexible Cable Assemblies

PE-SF200LL75 Coax, 75 Ohm

Part No. PE3TC1203				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			28
24"	36"	48"	72"	100CM	200CM	Custom Len.	
$94.44	$106.82	$117.55	$141.95	$108.77	$148.82	See Web	

Cable Assemblies

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

75 OHM F MALE TO 75 OHM F FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG179B/U Coax, 75 Ohm

Part No. PE3C5570				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft		29
12"	24"	36"	48"	60"	-	Custom Len.	
$29.86	$32.49	$35.10	$37.73	$40.37	-	See Web	

PE-B159-BL Coax, 75 Ohm

Part No. PE38138				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.159" dia.	10.5 dB/100ft		30
12"	24"	36"	48"	60"	72"	Custom Len.	
$31.54	$33.20	$34.85	$36.53	$38.19	$39.86	See Web	

75 OHM F FEMALE TO 75 OHM F FEMALE

Low Loss Flexible Cable Assemblies

PE-SF200LL75 Coax, 75 Ohm

Part No. PE3TC1206				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.195" dia.			31
24"	36"	48"	72"	100CM	200CM	Custom Len.	
$94.44	$106.82	$117.55	$141.95	$108.77	$148.82	See Web	

75 OHM MINI SMB PLUG TO 75 OHM BNC MALE

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE34701				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	32
12"	24"	36"	48"	60"	72"	Custom Len.	
$52.72	$53.87	$51.87	$52.91	$56.89	$54.56	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE34703				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	33
12"	24"	36"	48"	60"	72"	Custom Len.	
$58.83	$61.64	$64.46	$67.43	$65.91	$68.51	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE34705				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	34
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.96	$60.30	$64.04	$72.81	$71.52	$75.26	See Web	

PE-B159-BK Coax, 75 Ohm

Part No. PE38040				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.159" dia.	10.5 dB/100ft		35
12"	24"	36"	48"	60"	72"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

75 OHM MINI SMB PLUG TO 75 OHM MINI SMB PLUG

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE34681				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	36
12"	24"	36"	48"	60"	72"	Custom Len.	
$56.32	$57.31	$58.29	$59.30	$60.28	$61.27	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE34683				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	37
12"	24"	36"	48"	60"	72"	Custom Len.	
$59.37	$61.95	$64.55	$67.15	$69.76	$77.27	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE34685				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	38
12"	24"	36"	48"	60"	72"	Custom Len.	
$57.00	$60.61	$64.24	$73.25	$71.43	$75.04	See Web	

PE-B159-BL Coax, 75 Ohm

Part No. PE38139				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.159" dia.	10.5 dB/100ft		39
12"	24"	36"	48"	60"	72"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

75 OHM MINI SMB PLUG TO 75 OHM MINI SMB PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE34687				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	40
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.56	$65.56	$66.53	$67.55	$68.53	$74.24	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE34689				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	41
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.40	$68.39	$71.03	$73.68	$76.25	$78.89	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE34690				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	42
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.81	$70.44	$74.08	$77.62	$81.26	$84.89	See Web	

PE-B159-BL Coax, 75 Ohm

Part No. PE38140				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.159" dia.	10.5 dB/100ft		43
12"	24"	36"	48"	60"	72"	Custom Len.	
$82.05	$83.70	$85.36	$87.00	$88.66	$90.29	See Web	

75 OHM MINI SMB PLUG TO 75 OHM MINI SMB JACK

Standard Flexible Cable Assemblies

PE-B159-BL Coax, 75 Ohm

Part No. PE38141				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.159" dia.	10.5 dB/100ft		44
12"	24"	36"	48"	60"	72"	Custom Len.	
Call	Call	Call	Call	Call	Call	See Web	

75 OHM MINI SMB PLUG TO 75 OHM TNC MALE

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE3C6086				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	45
12"	24"	36"	48"	60"	50CM	Custom Len.	
$57.53	$58.63	$59.74	$60.85	$61.96	$58.23	See Web	

75 OHM MINI SMB PLUG RIGHT ANGLE TO 75 OHM F FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

RG187A/U Coax, 75 Ohm

Part No. PE3W07602				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.102" dia.		200 W	46
12"	24"	36"	48"	60"	50CM	Custom Len.	
$53.50	$57.58	$62.14	$66.72	$71.27	$55.94	See Web	

75 OHM MINI SMB PLUG RIGHT ANGLE TO 75 OHM MINI SMB PLUG RIGHT ANGLE

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE34692				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	47
12"	24"	36"	48"	60"	72"	Custom Len.	
$79.34	$80.34	$81.33	$82.32	$83.29	$84.29	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE34694				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	48
12"	24"	36"	48"	60"	72"	Custom Len.	
$83.54	$78.56	$89.16	$83.77	$86.36	$88.95	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE34696				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	49
12"	24"	36"	48"	60"	72"	Custom Len.	
$70.04	$73.68	$77.24	$80.86	$84.49	$88.12	See Web	

75 OHM N MALE TO 75 OHM BNC MALE

Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm

Part No. PE3341				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	125 W	50
12"	24"	36"	48"	60"	72"	Custom Len.	
$61.83	$61.29	$64.23	$67.16	$70.11	$73.05	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

RG11A/U Coax, 75 Ohm

Part No. PE3396				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	51
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$72.35	$74.19	$76.05	$77.84	$79.69	$81.45	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE33605				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	52
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$53.70	$54.25	$55.32	$60.94	$57.42	$63.27	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE3398				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	53
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.68	$67.28	$74.18	$77.16	$80.01	$82.88	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE3400				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	54
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$62.05	$65.61	$69.25	$72.89	$76.50	$80.14	See Web	

75 OHM N MALE TO 75 OHM F MALE

Low Loss Flexible Cable Assemblies

PE-SF200LL75 Coax, 75 Ohm

Part No. PE3TC1205				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	55
1 piece price shown. See web or call for volume pricing.				0.195" dia.			
24"	36"	48"	72"	100CM	200CM	Custom Len.	
$128.07	$140.28	$152.49	$176.89	$143.72	$183.76	See Web	

Standard Flexible Cable Assemblies

PE-75Test.35 Coax, 75 Ohm

Part No. PE3CA1031				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	56
1 piece price shown. See web or call for volume pricing.				0.3" dia.			
40CM	60CM	100CM	-	-	-	Custom Len.	
Call	$284.41	Call	-	-	-	See Web	

75 OHM N MALE TO 75 OHM F FEMALE

Low Loss Flexible Cable Assemblies

PE-SF200LL75 Coax, 75 Ohm

Part No. PE3TC1204				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	57
1 piece price shown. See web or call for volume pricing.				0.195" dia.			
24"	36"	48"	72"	100CM	200CM	Custom Len.	
$128.07	$140.28	$152.49	$176.89	$143.72	$183.76	See Web	

75 OHM N MALE TO 75 OHM N MALE

Low Loss Flexible Cable Assemblies

PE-SF200LL75 Coax, 75 Ohm

Part No. PE3TC1200				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	58
1 piece price shown. See web or call for volume pricing.				0.195" dia.			
6"	12"	24"	36"	48"	72"	Custom Len.	
		$163.01	$175.22	$187.43	$211.83	See Web	

Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm

Part No. PE3612				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	59
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	125 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.63	$69.56	$72.52	$75.46	$78.40	$81.34	See Web	

RG11A/U Coax, 75 Ohm

Part No. PE3616				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	60
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$75.86	$84.19	$86.47	$88.87	$91.19	$84.96	See Web	

RG59B/U Coax, 75 Ohm

Part No. PE3528				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	61
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$66.75	$71.88	$68.84	$69.90	$75.40	$76.57	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE3307				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	62
1 piece price shown. See web or call for volume pricing.				0.1" dia.	29.15 dB/100ft		
12"	24"	36"	48"	60"	72"	Custom Len.	
$77.82	$80.42	$83.00	$85.63	$88.22	$96.81	See Web	

RG187A/U Coax, 75 Ohm

Part No. PE3581				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	63
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$74.40	$84.56	$81.60	$85.22	$88.85	$92.49	See Web	

PE-75Test.35 Coax, 75 Ohm

Part No. PE3CA1032				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	64
1 piece price shown. See web or call for volume pricing.				0.3" dia.			
60CM	80CM	90CM	100CM	-	-	Custom Len.	
$323.03	Call	Call	Call	-	-	See Web	

75 OHM N MALE TO 75 OHM N FEMALE

Low Loss Flexible Cable Assemblies

PE-SF200LL75 Coax, 75 Ohm

Part No. PE3TC1201				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	65
1 piece price shown. See web or call for volume pricing.				0.195" dia.			
24"	36"	48"	72"	100CM	200CM	Custom Len.	
$158.04	$170.25	$182.45	$206.87	$173.67	$213.72	See Web	

75 OHM N FEMALE TO 75 OHM N FEMALE

Standard Flexible Cable Assemblies

RG11A/U Coax, 75 Ohm

Part No. PE3W04530				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	66
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W	
12"	24"	36"	48"	60"	50CM	Custom Len.	
$95.71	$98.14	$100.57	$103.02	$105.45	$97.27	See Web	

75 OHM RCA MALE TO 75 OHM RCA MALE

Standard Flexible Cable Assemblies

PE-B159-BL Coax, 75 Ohm

Part No. PE38133				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	67
1 piece price shown. See web or call for volume pricing.				0.159" dia.	10.5 dB/100ft		
12"	24"	36"	48"	60"	72"	Custom Len.	
$50.91	$52.59	$54.23	$55.39	$57.05	$58.70	See Web	

75 OHM RCA MALE TO 75 OHM RCA MALE RIGHT ANGLE

Standard Flexible Cable Assemblies

PE-B159-BL Coax, 75 Ohm

Part No. PE38134				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	68
1 piece price shown. See web or call for volume pricing.				0.159" dia.	10.5 dB/100ft		
12"	24"	36"	48"	60"	72"	Custom Len.	
$54.12	$55.27	$56.91	$58.56	$60.21	$61.86	See Web	

75 OHM RCA MALE TO 75 OHM RCA FEMALE BULKHEAD

SEE MOUNTING HOLE SECTION ON PAGE 409

Standard Flexible Cable Assemblies

PE-B159-BL Coax, 75 Ohm

Part No. PE38135				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	69
1 piece price shown. See web or call for volume pricing.				0.159" dia.	10.5 dB/100ft		
12"	24"	36"	48"	60"	72"	Custom Len.	
$50.91	$52.59	$54.23	$55.39	$57.05	$58.70	See Web	

75 OHM SMB PLUG TO 75 OHM BNC MALE

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm

Part No. PE33270				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	70
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$57.97	$59.11	$60.26	$56.85	$57.90	$58.94	See Web	

RG179B/U Coax, 75 Ohm

Part No. PE33247				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	71
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$63.15	$61.07	$68.78	$71.75	$74.62	$77.47	See Web	

PE-B150 Coax, 75 Ohm

Part No. PE33644				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz	72
1 piece price shown. See web or call for volume pricing.				0.15" dia.	20 dB/100ft	25 W	
12"	24"	36"	48"	60"	72"	Custom Len.	
$64.39	$65.26	$66.13	$67.00	$67.87	$68.74	See Web	

See Our Website For Current Pricing & Real-Time Stock Availability!

*Coax Performance at 1 GHz Notes: Cable assembly max frequency may be lower than connector or coax max frequency

75 OHM SMB PLUG TO 75 OHM SMB PLUG

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm — 73

Part No. PE3041				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$65.83	$66.88	$67.94	$69.00	$70.04	$71.10	See Web

RG179B/U Coax, 75 Ohm — 74

Part No. PE3100				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	29.15 dB/100ft	
12"	24"	36"	48"	60"	72"	Custom Len.
$59.62	$67.19	$64.83	$67.45	$70.11	$78.72	See Web

PE-B150 Coax, 75 Ohm — 75

Part No. PE3112				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.15" dia.	20 dB/100ft	25 W
12"	24"	36"	48"	60"	72"	Custom Len.
$64.44	$65.23	$66.10	$66.87	$67.72	$68.53	See Web

75 OHM SMC PLUG TO 75 OHM BNC MALE

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm — 76

Part No. PE33330				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$51.14	$54.85	$53.28	$54.34	$58.37	$55.95	See Web

RG179B/U Coax, 75 Ohm — 77

Part No. PE33586				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W
12"	24"	36"	48"	60"	72"	Custom Len.
$66.14	$64.99	$71.76	$70.18	$77.60	$80.46	See Web

PE-B150 Coax, 75 Ohm — 78

Part No. PE33646				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.15" dia.	20 dB/100ft	25 W
12"	24"	36"	48"	60"	72"	Custom Len.
$69.49	$74.69	$71.23	$72.11	$72.97	$78.83	See Web

75 OHM SMC PLUG TO 75 OHM SMC PLUG

Standard Flexible Cable Assemblies

RG59B/U Coax, 75 Ohm — 79

Part No. PE3362				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$62.50	$63.56	$71.05	$65.66	$66.73	$67.77	See Web

RG179B/U Coax, 75 Ohm — 80

Part No. PE3376				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W
12"	24"	36"	48"	60"	72"	Custom Len.
$64.83	$67.40	$70.04	$72.61	$75.26	$77.89	See Web

PE-B150 Coax, 75 Ohm — 81

Part No. PE3388				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.15" dia.	20 dB/100ft	25 W
12"	24"	36"	48"	60"	72"	Custom Len.
$78.53	$84.26	$80.27	$81.13	$82.01	$82.87	See Web

75 OHM TNC MALE TO 75 OHM BNC MALE

Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm — 82

Part No. PE35350				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	125 W
12"	24"	36"	48"	60"	72"	Custom Len.
$55.79	$55.58	$58.52	$61.46	$64.41	$67.35	See Web

RG11A/U Coax, 75 Ohm — 83

Part No. PE35354				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W
12"	24"	36"	48"	60"	72"	Custom Len.
$88.02	$89.93	$91.79	$93.69	$95.58	$97.46	See Web

RG59B/U Coax, 75 Ohm — 84

Part No. PE35358				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$48.38	$49.43	$50.49	$51.55	$52.62	$56.62	See Web

RG179B/U Coax, 75 Ohm — 85

Part No. PE35362				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W
12"	24"	36"	48"	60"	72"	Custom Len.
$63.54	$66.34	$64.03	$66.64	$69.23	$71.82	See Web

RG187A/U Coax, 75 Ohm — 86

Part No. PE35366				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W
12"	24"	36"	48"	60"	72"	Custom Len.
$55.44	$59.09	$62.72	$66.27	$69.91	$73.53	See Web

75 OHM TNC MALE TO 75 OHM TNC MALE

Standard Flexible Cable Assemblies

RG6A/U Coax, 75 Ohm — 87

Part No. PE35348				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.332" dia.	11 dB/100ft	125 W
12"	24"	36"	48"	60"	72"	Custom Len.
$58.54	$61.48	$64.43	$67.36	$70.31	$73.25	See Web

RG11A/U Coax, 75 Ohm — 88

Part No. PE35352				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.405" dia.		150 W
12"	24"	36"	48"	60"	72"	Custom Len.
$97.17	$98.94	$100.78	$102.56	$104.41	$106.27	See Web

RG59B/U Coax, 75 Ohm — 89

Part No. PE35356				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.242" dia.	11.5 dB/100ft	77 W
12"	24"	36"	48"	60"	72"	Custom Len.
$56.19	$60.70	$61.85	$59.36	$60.40	$65.38	See Web

RG179B/U Coax, 75 Ohm — 90

Part No. PE35360				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.1" dia.	25 dB/100ft	200 W
12"	24"	36"	48"	60"	72"	Custom Len.
$71.53	$68.83	$71.43	$74.04	$76.64	$85.86	See Web

RG187A/U Coax, 75 Ohm — 91

Part No. PE35364				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W
12"	24"	36"	48"	60"	72"	Custom Len.
$61.27	$64.83	$68.47	$72.11	$75.71	$79.34	See Web

75 OHM BNC MALE TO STRAIGHT CUT LEAD SEXLESS

Flexible Cable Assemblies

RG187A/U Coax, 75 Ohm — 92

Part No. PE39599				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.11" dia.	25 dB/100ft	200 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$48.62	$53.44	$53.98	$54.56	$55.62	$49.27	See Web

BNC TWINAX PLUG TO BNC TWINAX PLUG

Standard Flexible Cable Assemblies

RG108A/U Coax, 78 Ohm — 93

Part No. PE3480				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.235" dia.	26.2 dB/100ft	30 W
18"	36"	60"	90"	120"	180"	Custom Len.
$83.32	$87.43	$93.12	$119.37	$107.11	$119.39	See Web

3/4"-20 TWINAX MALE TO 3/4"-20 TWINAX MALE

Standard Flexible Cable Assemblies

PE-S330 Coax, 100 Ohm — 94

Part No. PE3930				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.33" dia.		
18"	36"	60"	90"	120"	180"	Custom Len.
$88.28	$92.66	$98.50	$105.80	$111.52	$125.91	See Web

BANANA PLUG TO SMA MALE

Standard Flexible Cable Assemblies

RG188-DS Coax, 50 Ohm — 95

Part No. PE3W06020				Cable Dia.	Attn. @ 1 GHz	Power @ 1 GHz
1 piece price shown. See web or call for volume pricing.				0.118" dia.	30 dB/100ft	160 W
12"	24"	36"	48"	60"	50CM	Custom Len.
$41.59	$45.70	$49.79	$53.89	$57.47	$44.22	See Web

See Our Website For Current Pricing & Real-Time Stock Availability!

CIRCULATORS AND ISOLATORS

Circulators

Dual Junction

Connector	Frequency Range (MHz.)	Maximum Power	VSWR Max.	Isolation (dB Min.)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
N	1,000 - 2,000	50 Watt	1.35:1	36	PE83CR1014	$1,523.70		See Web for Volume Pricing		1
	1,700 - 2,200		1.25:1	40	PE83CR1016	$907.52				2
	2,000 - 4,000		1.3:1		PE83CR1018	$911.36				3
	4,000 - 8,000	10 Watt		36	PE83CR1020	$692.23				4
	7,000 - 12,400	5 Watt		40	PE83CR1022	$643.64				5
SMA	1,000 - 2,000	50 Watt	1.35:1	36	PE83CR1013	$1,793.42				6
	1,700 - 2,200		1.25:1	40	PE83CR1015	$942.92				7
	2,000 - 4,000		1.3:1		PE83CR1017	$838.00				8
	4,000 - 8,000	10 Watt		36	PE83CR1019	$875.89				9
	7,000 - 12,400	5 Watt		40	PE83CR1021	$643.64				10
	8,000 - 18,000		1.45:1	32	PE83CR1023	$862.87				11
	11,000 - 18,000		1.25:1	40	PE83CR1024	$835.96				12
	18,000 - 26,500		1.4:1	34	PE83CR1025	$938.62				13

Single Junction

Connector	Frequency Range (MHz.)	Maximum Power	VSWR Max.	Isolation (dB Min.)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
2.92mm	18,000 - 26,500	10 Watt	1.8:1	12	PE83CR1027	$1,044.68		See Web for Volume Pricing		14
	22,000 - 33,000		1.7:1	13	PE83CR1028	$1,002.04				15
	26,500 - 40,000		1.8:1	12	PE83CR1032	$1,133.02				16
	32,000 - 36,000			14	PE83CR1029	$1,075.15				17
N	135 - 175	150 Watt	1.3:1	20	PE8427	$1,602.97				18
	330 - 403		1.25:1		PE8429	$1,428.51				19
	380 - 460	1000 Watt			PE8423	$555.01				20
	450 - 520	150 Watt			PE8431	$1,365.49				21
	698 - 960	1000 Watt	1.3:1	18	PE8419	$456.10				22
	1,000 - 2,000	10 Watt	1.35:1		PE8410	$1,024.77				23
	1,000 - 2,000	100 Watt			PE83CR1001	$1,218.25				24
	1,700 - 2,200	10 Watt	1.25:1		PE8415	$470.11				25
	1,700 - 2,200	100 Watt		20	PE83CR1003	$754.98				26
	2,000 - 4,000	10 Watt	1.3:1	18	PE8411	$756.13				27
	2,000 - 4,000	100 Watt		20	PE83CR1005	$727.71				28
	2,000 - 4,000		1.35:1	18	PE83CR1031	$386.82				29
	4,000 - 8,000	10 Watt	1.3:1		PE8412	$632.95				30
	4,000 - 8,000	50 Watt			PE83CR1007	$573.93				31
	7,000 - 12,400	10 Watt	1.25:1	20	PE8413	$542.32				32
	7,000 - 12,400	50 Watt			PE83CR1009	$472.04				33
SMA	135 - 175	150 Watt	1.3:1	20	PE8426	$1,635.02				34
	330 - 403		1.25:1		PE8428	$1,484.22				35
	380 - 460	1000 Watt			PE8422	$546.82				36
	450 - 520	150 Watt			PE8430	$1,365.49				37
	698 - 960	1000 Watt	1.3:1	18	PE8418	$475.39				38
	700 - 800	10 Watt	1.25:1		PE83CR001	$205.75				39
	800 - 960			19	PE83CR007	$262.42				40
	1,000 - 2,000		1.35:1	17	PE83CR003	$315.62				41
	1,000 - 2,000			18	PE8400	$774.63				42
	1,000 - 2,000	100 Watt			PE83CR1000	$1,218.25				43
	1,700 - 2,200	10 Watt	1.25:1		PE8414	$498.71				44
	1,700 - 2,200	100 Watt		20	PE83CR1002	$725.95				45

See Our Website For Current Pricing & Real-Time Stock Availability!

Circulators

Single Junction

Connector	Frequency Range (MHz.)	Maximum Power	VSWR Max.	Isolation (dB Min.)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
SMA	1,700 - 2,400	10 Watt	1.3:1	17	PE83CR004	$201.97		See Web for Volume Pricing		46
	2,000 - 4,000				PE83CR005	$252.73				47
	2,000 - 4,000		1.3:1	18	PE8401	$465.88				48
	2,000 - 4,000	100 Watt		20	PE83CR1004	$686.92				49
	2,000 - 4,000		1.35:1	18	PE83CR1030	$417.27				50
	2,000 - 6,000	25 Watt	1.5:1	14	PE8432	$932.00				51
	3,000 - 5,000	10 Watt	1.3:1	18	PE83CR1033	$466.00				52
	4,000 - 8,000		1.35:1	17	PE83CR006	$252.29				53
	4,000 - 8,000		1.3:1	18	PE8402	$328.70				54
	4,000 - 8,000	50 Watt			PE83CR1006	$654.16				55
	4,000 - 8,000	80 Watt	1.4:1	17	PE83CR1034	$435.55				56
	6,000 - 18,000	10 Watt	1.5:1	14	PE8433	$868.32				57
	7,000 - 12,400		1.3:1	18	PE83CR000	$210.06				58
	7,000 - 12,400				PE8403	$303.37				59
	7,000 - 12,400	50 Watt	1.25:1	20	PE83CR1008	$490.45				60
	8,000 - 12,000	10 Watt	1.5:1	18	PE83CR1026	$539.10				61
	8,000 - 18,000		1.55:1	13	PE83CR002	$315.62				62
	8,000 - 18,000		1.45:1	16	PE8404	$367.00				63
	8,000 - 18,000	50 Watt			PE83CR1010	$497.09				64
	11,000 - 18,000	10 Watt	1.25:1	20	PE8405	$404.60				65
	11,000 - 18,000	50 Watt			PE83CR1011	$539.76				66
	18,000 - 26,500	10 Watt	1.4:1	17	PE8406	$375.33				67
	18,000 - 26,500	50 Watt			PE83CR1012	$558.92				68

Isolators

Dual Junction

Connector	Frequency Range (MHz.)	Maximum Power	VSWR Max.	Isolation (dB Min.)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
N	1,000 - 2,000	50 Watt	1.35:1	36	PE83IR1014	$1,525.43		See Web for Volume Pricing		69
	1,700 - 2,200		1.25:1	40	PE83IR1016	$880.41				70
	2,000 - 4,000		1.3:1		PE83IR1018	$858.84				71
	4,000 - 8,000	10 Watt		36	PE83IR1020	$725.65				72
	7,000 - 12,400	5 Watt	1.25:1	40	PE83IR1022	$625.01				73
SMA	1,000 - 2,000	50 Watt	1.35:1	36	PE83IR1013	$1,525.43				74
	1,700 - 2,200		1.25:1	40	PE83IR1015	$928.44				75
	2,000 - 4,000		1.3:1		PE83IR1017	$874.80				76
	4,000 - 8,000	10 Watt		36	PE83IR1019	$811.73				77
	7,000 - 12,400	5 Watt	1.25:1	40	PE83IR1021	$917.73				78
	8,000 - 18,000		1.45:1	32	PE83IR1023	$883.61				79
	11,000 - 18,000		1.25:1	40	PE83IR1024	$823.11				80
	18,000 - 26,500		1.4:1	34	PE83IR1025	$946.99				81

Single Junction

Connector	Frequency Range (MHz.)	Maximum Power	VSWR Max.	Isolation (dB Min.)	Model No	1-4	5-9	10-24	25+	ROW
2.4mm	35,000 - 42,500	10 Watt	1.6:1	14	PE83IR1038	$1,038.61	$986.68	$934.75	$893.20	82
2.92mm	18,000 - 26,500	10 Watt	1.7:1	14	PE83IR1033	$817.17	$776.31	$735.45	$702.77	83
	18,000 - 26,500				PE83IR1041	$1,771.57	$1,682.99	$1,594.41	$1,523.55	84

See Our Website For Current Pricing & Real-Time Stock Availability!

Isolators

Single Junction

Connector	Frequency Range (MHz.)	Maximum Power	VSWR Max.	Isolation (dB Min.)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
2.92mm	22,000 - 33,000	10 Watt	1.8:1	13	PE83IR1035	$817.17				85
	26,500 - 40,000	5 Watt	1.5:1	14	PE8320	$1,228.00				86
	26,500 - 40,000	10 Watt	1.7:1	12	PE83IR1036	$817.17				87
	26,500 - 40,000				PE83IR1037	$817.17				88
	27,000 - 31,000	5 Watt	1.25:1	20	PE8319	$1,117.19				89
N	135 - 175	150 Watt	1.3:1	20	PE8322	$1,641.50				90
	330 - 403		1.25:1		PE8324	$1,121.98				91
	380 - 460	100 Watt			PE8425	$581.69				92
	450 - 520	150 Watt			PE8326	$1,063.94				93
	698 - 960	1000 Watt	1.3:1	18	PE8421	$505.88				94
	1,000 - 2,000	10 Watt	1.35:1		PE8310	$1,215.87				95
	1,000 - 2,000			17	PE83IR003	$432.91				96
	1,000 - 2,000	100 Watt		18	PE83IR1001	$1,346.60				97
	1,700 - 2,200	10 Watt	1.25:1		PE8417	$278.99				98
	1,700 - 2,200	100 Watt		20	PE83IR1003	$791.43				99
	2,000 - 4,000	10 Watt	1.3:1	18	PE8311	$759.13				1
	2,000 - 4,000	100 Watt		20	PE83IR1005	$751.36				2
	4,000 - 8,000	10 Watt		18	PE8312	$648.15				3
	4,000 - 8,000	50 Watt			PE83IR1007	$661.52				4
	7,000 - 12,400	10 Watt	1.25:1	20	PE8313	$822.41				5
SMA	135 - 175	150 Watt	1.3:1	20	PE8321	$1,857.38	See Web for Volume Pricing			6
	330 - 403		1.25:1		PE8323	$1,519.90				7
	380 - 460	100 Watt			PE8424	$543.62				8
	450 - 520	150 Watt			PE8325	$1,398.32				9
	698 - 960	1000 Watt	1.3:1	18	PE8420	$478.12				10
	800 - 900	100 Watt	1.25:1	20	PE83IR007	$245.81				11
	1,000 - 2,000	10 Watt	1.35:1	18	PE8300	$769.90				12
	1,000 - 2,000		1.4:1	17	PE83IR002	$340.96				13
	1,000 - 2,000		1.5:1	16	PE83IR1032	$714.25				14
	1,000 - 2,000	100 Watt	1.35:1	18	PE83IR1000	$1,292.00				15
	1,700 - 2,200	10 Watt	1.25:1		PE8416	$510.69				16
	1,700 - 2,200	100 Watt		20	PE83IR1002	$803.28				17
	1,700 - 2,400	10 Watt	1.35:1	18	PE83IR004	$238.20				18
	2,000 - 4,000		1.3:1		PE8301	$627.29				19
	2,000 - 4,000		1.4:1		PE83IR005	$331.41				20
	2,000 - 4,000	100 Watt	1.3:1	20	PE83IR1004	$745.21				21
	2,000 - 6,000	10 Watt	1.8:1	12	PE83IR1039	$483.45				22
	2,000 - 6,000	25 Watt	1.5:1	14	PE8327	$863.07				23
	2,000 - 8,000	10 Watt	1.35:1	15	PE8316	$1,407.36				24
	2,000 - 10,000			13	PE8317	$1,407.36				25
	3,500 - 12,800	2 Watt	1.5:1	17	PE8314	$1,301.92				26
	4,000 - 8,000	10 Watt	1.3:1	18	PE8302	$359.79				27
	4,000 - 8,000		1.35:1		PE83IR006	$328.28				28
	4,000 - 8,000	30 Watt		19	PE83IR1040	$489.68				29
	4,000 - 8,000	50 Watt	1.3:1	18	PE83IR1006	$549.27				30
	4,000 - 18,000	10 Watt	1.5:1	15	PE8315	$1,357.58				31
	6,000 - 18,000			14	PE8328	$1,099.00				32
	6,000 - 18,000		1.6:1	10	PE83IR1029	$548.95				33
	6,000 - 18,000				PE83IR1030	$548.95				34
	6,000 - 18,000				PE83IR1031	$548.95				35
	7,000 - 12,400	1 Watt	1.3:1	18	PE8303	$317.32				36
	7,000 - 12,400	10 Watt			PE83IR000	$310.71				37
	8,000 - 12,000		1.35:1	20	PE83IR1026	$424.18				38
	8,000 - 12,000				PE83IR1027	$424.18				39
	8,000 - 18,000	1 Watt	1.45:1	16	PE8304	$337.34				40
	8,000 - 18,000	10 Watt	1.5:1		PE83IR001	$304.80				41
	8,000 - 18,000	50 Watt	1.45:1		PE83IR1010A	$501.52				42
	11,000 - 18,000	1 Watt	1.25:1	20	PE8305	$309.49				43
	11,000 - 18,000	50 Watt			PE83IR1011	$524.32				44
	12,000 - 18,000	10 Watt	1.35:1		PE83IR1028	$449.14				45
	17,300 - 22,000		1.25:1		PE8318	$637.94				46
	18,000 - 26,500	1 Watt	1.4:1	17	PE8306	$311.48				47
	18,000 - 26,500	10 Watt	1.7:1	14	PE83IR1034	$804.69				48
	18,000 - 26,500	50 Watt	1.4:1	17	PE83IR1012	$594.68				49

See Our Website For Current Pricing & Real-Time Stock Availability!

INDEX GUIDE TO
COAXIAL CABLES



COAXIAL CABLES.....225

75 OHM BROADCAST.....226

Pasternack's selection of 75 Ohm Broadcast coaxial cable includes RG59-P plenum cable, commercial grade RG6-CATV, HD mini 59 cable in multiple colors as well as PTFE jacketed RG187A/U.

RG MIL-C-17 TYPE CABLE.....227

Pasternack offers 31 different MIL-C-17 compliant coaxial cable types. These cables are available in various diameters, jacket materials, impedances, and velocity factors, providing numerous RF cable options to fit your specific requirements.

COMMUNICATIONS.....226

Our selection of Low Loss cable is designed with high Velocity Factor (VF) dielectric materials and two outer shields for communications applications requiring Low Loss and High Isolation. These cables are offered in several popular sizes including 0.195", 0.240", 0.400", and 0.600" diameters.

SEMIRIGID AND FORMABLE.....228

Pasternack's Precision Cables are designed for RF and Microwave applications with frequencies up to 65 GHz. These cables are constructed of copper jacketed and tinned aluminum semirigid designs; and tinned braid conformable cable in both FEP jacketed and unjacketed designs. The semi rigid and conformable cables are available from 0.020 to 0.250 inches in diameter.



HIGH PERFORMANCE.....227

Pasternack's line of High Performance Flexible Cable has high Velocity Factors of 70 to 85% and incorporate Spiral Wrapped outer conductors for superior shielding under flexure. These cables are used as flexible cable alternatives to semirigid cable and in many cases use the same connectors.

TWINAX.....230

Pasternack offers two versions of Twinax cable with an impedance of 100 or 78 ohms. Twinax cable has two center conductors surrounded by a dielectric. The dielectric is surrounded by a braided outer conductor covered by a PVC jacket material. This construction creates a shielded, twisted pair with superior performance when compared to unshielded, twisted pair cable.

COAXIAL CABLES

Meets or Exceeds MIL-C-17 Specifications Where Applicable

MODEL NO.	COAX IMPEDANCE (Ohm) MAXIMUM FREQUENCY (GHz.)	JACKET DIAMETER (in) CONDUCTOR DIAM.(in) [strands]	NUMBER OF SHIELDS RF SHIELDING (min dB)	VELOCITY FACTOR (%) ATTENUATION AT 1 GHz. (dB/100 ft)	MAX. POWER HANDLING AT 1 GHz (W) MAXIMUM OPERATING VOLTAGE (V RMS)	JACKET MATERIAL MINIMUM BEND RADIUS (in)	PRICE PER FOOT 1-99 FT 500-999 FT	PRICE PER FOOT 100-499 FT 1000 + FT	ROW
75 OHM BROADCAST									
LMR-400-75	75 2.5	0.405 0.065[1]	2 90	85		PE 1	$1.36 $1.36	$1.36 $1.36	1
PE-B150	75 5	0.150 0.017[7]	1	20	25 600	PVC	$1.20 $1.08	$1.14 $1.03	2
PE-B159-BK	75 3	0.159 0.023[1]	2	83 10.5	300	PVC 1.5	$1.17 $1.05	$1.11 $1.01	3
PE-B159-BL	75 3	0.159 0.023[1]	2	83 10.5	300	PVC 1.5	$1.24 $1.12	$1.18 $1.07	4
PE-B159-GR	75 3	0.159 0.023[1]	2	83 10.5	300	PVC 1.5	$1.01 $0.91	$0.96 $0.87	5
PE-B159-RD	75 3	0.159 0.023[1]	2	83 10.5	300	PVC 1.5	$1.05 $0.95	$1.00 $0.90	6
PE-B159-WH	75 3	0.159 0.023[1]	2	83 10.5	300	PVC 1.5	$0.95 $0.86	$0.90 $0.82	7
PE-B159-YW	75 3	0.159 0.023[1]	2	83 10.5	300	PVC 1.5	$1.00 $0.90	$0.95 $0.86	8
PE-B305	75 1	0.305 0.031[1]	2	9.2	52 2,900	PVC	$3.04 $2.74	$2.89 $2.61	9
RG11A/U	75 1	0.405 [7]	1 45	66 8.11	150	PVC	$2.60 $2.34	$2.47 $2.24	10
RG179B/U	75 3	0.100 0.012[7]	1	70 29.15	900	FEP	$3.16 $2.84	$3.00 $2.72	11
RG187A/U	75 3	0.102 0.012[7]	1	70 25	200 2,000	PTFE	$4.96 $4.46	$4.71 $4.27	12
RG302/U	75 3	0.206 0.025[7]	1	69 13	650 1,700	FEP	$8.26 $7.43	$7.85 $7.10	13
RG59B/U	75 1	0.242 0.022[1]	1	66 11.5	77 2,300	PVC (NC)	$1.18 $1.06	$1.12 $1.01	14
RG6A/U	75 1	0.332 0.029[1]	2 90	66 11	100	PVC (NC)	$6.37 $5.73	$6.05 $5.48	15
RG6-CATV	75 3	0.278 0.04[1]	3 70	85 6.55	6.5	PVC (NC)	$1.57 $1.41	$1.49 $1.35	16
COMMUNICATIONS									
LMR-200-UF	50 5.8	0.195 0.044	2 90	83 12.18		TPE 0.5	$2.22 $2.22	$2.22 $2.22	17
LMR-100A-PVC	50 5.8	0.110 0.018[1]	2 90	66 24		PVC 0.25	$0.77 $0.77	$0.77 $0.77	18
LMR-195	50 5.8	0.195 0.037[1]	2 90	80 11.8		PE 0.5	$0.67 $0.67	$0.67 $0.67	19
LMR-195-FR	50 5.8	0.195 0.037[1]	2 90	76 11.8		FRPE 0.5	$1.05 $1.05	$1.05 $1.05	20
LMR-195-LLPL	50 8	0.195 0.037[1]	2 90	80 11.8		PVC (FR) 0.5	$8.29 $8.29	$8.29 $8.29	21
LMR-200	50 5.8	0.195 0.044[1]	2 90	83 10.5		PE 0.5	$0.75 $0.75	$0.75 $0.75	22
LMR-200-FR	50 5.8	0.195 0.044[1]	2 90	83		FRPE 0.5	$1.06 $1.06	$1.06 $1.06	23
LMR-240	50 5.8	0.240 0.056[1]	2 90	84 8		PE 0.75	$0.92 $0.92	$0.92 $0.92	24
LMR-240-DB	50 5.8	0.240 0.056[1]	2 90	84 7.66		PE 0.75	$1.06 $1.06	$1.06 $1.06	25
LMR-240-UF	50 5.8	0.240 0.056	2 90	84 9.19		TPE 0.75	$1.12 $1.12	$1.12 $1.12	26
LMR-400	50 6	0.405 0.108[1]	2 90	85 4.25		PE 1	$1.30 $1.30	$1.30 $1.30	27
LMR-400-DB	50 6	0.405 0.108[1]	2 90	85 4.15		PE 1	$1.39 $1.39	$1.39 $1.39	28

See Our Website For Current Pricing & Real-Time Stock Availability!

COAXIAL CABLES

Meets or Exceeds MIL-C-17 Specifications Where Applicable

MODEL NO.	COAX IMPEDANCE (Ohm) MAXIMUM FREQUENCY (GHz.)	JACKET DIAMETER (in) CONDUCTOR DIAM.(in) [strands]	NUMBER OF SHIELDS RF SHIELDING (min dB)	VELOCITY FACTOR (%) ATTENUATION AT 1 GHz. (dB/100 ft)	MAX. POWER HANDLING AT 1 GHz (W) MAXIMUM OPERATING VOLTAGE (V RMS)	JACKET MATERIAL MINIMUM BEND RADIUS (in)	PRICE PER FOOT 1-99 FT 500-999 FT	PRICE PER FOOT 100-499 FT 1000 + FT	ROW
COMMUNICATIONS									
LMR-400-UF	50 5.8	0.405 0.108	2 90	85 5		TPE 1	$1.88 $1.88	$1.88 $1.88	29
LMR-500	50 5.8	0.500 0.142[1]	2 90	86 3.1		PE 1.25	$2.06 $2.06	$2.06 $2.06	30
LMR-500-DB	50 5.8	0.500 0.142[1]	2 90	86 3.1		PE 1.25	$2.32 $2.32	$2.32 $2.32	31
LMR-600	50 5.8	0.590 0.176[1]	2 90	87 2.62		PE 1.5	$2.34 $2.34	$2.34 $2.34	32
LMR-600-DB	50 5.8	0.590 0.176[1]	2 90	87 2.62		PE 1.5	$2.81 $2.81	$2.81 $2.81	33
PE-1/2FAC	50 8.8	0.629 0.189[1]	1 120	88 2.2		PE 2.75	$5.76 $5.18	$5.47 $4.95	34
PE-1/2SFHC	50 10.2	0.519 0.141[1]	1 120	82 3.41	1,000	PE 0.6	$5.73 $5.16	$5.44 $4.93	35
PE-1/4SFHC	50 20.4	0.303 0.075[1]	1 120	82 5.85		PE 0.5	$3.98 $3.58	$3.78 $3.42	36
PE-B400	50 4	0.403 0.103[1]	2	6	190 600	PVC	$2.57 $2.31	$2.44 $2.21	37
PE-C100-LSZH	50 5.8	0.109 0.018[1]	2 90	66 25	40	LSZH 0.25	$1.67 $1.50	$1.59 $1.44	38
PE-C195	50 5.8	0.195 0.037[1]	2 90	80 11.7	135	PE 0.5	$0.91 $0.82	$0.86 $0.78	39
PE-C200	50 5.8	0.195 0.044[1]	2 90	83 10.8	170 1,000	PE	$1.10 $0.99	$1.05 $0.95	40
PE-C240	50 5.8	0.240 0.056[1]	2 90	84 7.98	250	PE 0.75	$1.49 $1.34	$1.42 $1.28	41
PE-C300	50 2.5	0.300 0.07[1]	2	85 6.3	350 2,000	PE 1.5	$3.74 $3.37	$3.55 $3.22	42
PE-C400	50 5.8	0.405 0.108[1]	2 90	85 4.1	480	PE	$1.66 $1.49	$1.58 $1.43	43
PE-C500	50 6	0.500 0.142[1]	2 90	86 3.5	720 3,000	PE	$5.73 $5.16	$5.44 $4.93	44
PE-C600	50 5.8	0.590 0.176[1]	2 90	87 2.7	900	PE	$3.00 $2.70	$2.85 $2.58	45
HIGH PERFORMANCE									
PE-P047	50 20	0.056 0.011[1]	2 90	70 35	43	FEP 0.2	$9.67 $8.70	$9.19 $8.32	46
PE-P086	50 18	0.104 0.02[1]	2 110	70 21.7		FEP	$10.61 $9.55	$10.08 $9.12	47
PE-P086HF	50 40	0.104 0.02[1]	2	70 21.1		FEP 0.52	$8.79 $7.91	$8.35 $7.56	48
PE-P141	50 18	0.163 0.037[1]	2 110	70 11.2	600	FEP	$14.43 $12.99	$13.71 $12.41	49
PE-P141HF	50 31	0.163 0.037[1]	2	70 13		FEP 0.82	$16.47 $14.82	$15.65 $14.16	50
PE-P142LL	50 18	0.195 0.051[1]	3	80 8.2	820	FEP	Call Call	Call Call	51
PE-P160LL	50 18	0.160 0.04[1]	3	83 11	560	FEP	Call Call	Call Call	52
PE-P195	50 22	0.195 0.037[1]	3	70 12.5	650 1,900	FEP	$12.73 $11.46	$12.09 $10.95	53
PE-P300LL	50 18	0.300 0.089[1]	3	83 5.1	1,700	FEP	Call Call	Call Call	54
RG MIL-C-17 TYPE CABLE									
RG141A/U	50 10	0.190 0.037[1]	1	70 13	650	PTFE (FG)	$8.17 $7.35	$7.76 $7.03	55

See Our Website For Current Pricing & Real-Time Stock Availability!

COAXIAL CABLES

Meets or Exceeds MIL-C-17 Specifications Where Applicable

MODEL NO.	COAX IMPEDANCE (Ohm) MAXIMUM FREQUENCY (GHz.)	JACKET DIAMETER (in) CONDUCTOR DIAM.(in) [strands]	NUMBER OF SHIELDS RF SHIELDING (min dB)	VELOCITY FACTOR (%) ATTENUATION AT 1 GHz. (dB/100 ft)	MAX. POWER HANDLING AT 1 GHz (W) MAXIMUM OPERATING VOLTAGE (V RMS)	JACKET MATERIAL MINIMUM BEND RADIUS (in)	PRICE PER FOOT 1-99 FT 500-999 FT	PRICE PER FOOT 100-499 FT 1000 + FT	ROW
RG MIL-C-17 TYPE CABLE									
RG142B/U	50 8	0.195 0.037[1]	2	70 12.9	1,900	FEP	$6.73 $6.06	$6.39 $5.79	56
RG174A/U	50 1	0.110 0.019[7]	1	66 32	17	PVC	$0.65 $0.59	$0.62 $0.56	57
RG178B/U	50 3	0.072 0.012[7]	1	70 44.41	55 1,000	FEP	$1.18 $1.06	$1.12 $1.01	58
RG180B/U	95 3	0.141 0.012[7]	1	70	250	FEP	$5.42 $4.88	$5.15 $4.66	59
RG188A/U	50 3	0.110 0.02[7]	1	26	160	PTFE	$3.20 $2.88	$3.04 $2.75	60
RG188-DS	50 10	0.118 0.02[7]	2	30	160	PTFE	$4.53 $4.08	$4.30 $3.90	61
RG196A/U	50 1	0.080 0.011[7]	1	49	78	PTFE	$1.70 $1.53	$1.62 $1.46	62
RG213/U	50 1	0.405 0.09[7]	1	66 9	190 3,700	PVC	$1.79 $1.64	$1.71 $1.60	63
RG214/U	50 11	0.425 0.089[7]	2	66 7.32	170 5,000	PVC	$9.41 $8.47	$8.94 $8.09	64
RG217/U	50 1	0.545 0.106[1]	2	66 5.8	260 5,200	PVC	$5.76 $5.18	$5.47 $4.95	65
RG218/U	50 1	0.870 0.195[1]	1	66 5	600 11,000	PVC	$14.61 $13.15	$13.88 $12.56	66
RG223/U	50 12.4	0.209 0.035[1]	2	66 13.41	50 1,900	PVC	$3.56 $3.20	$3.38 $3.06	67
RG225/U	50 10	0.430 0.094[7]	2	70 7.5	1,700 3,700	PTFE (FG)	$40.35 $36.32	$38.33 $34.70	68
RG303/U	50 3	0.170 0.037[1]	1	14	650	FEP	$7.74 $6.97	$7.35 $6.66	69
RG316/U	50 3	0.102 0.02[7]	1	69 38	900	FEP	$3.28 $2.95	$3.12 $2.82	70
RG316-DS	50 3	0.114 0.02[7]	2 85	70 29	120 1,200	FEP 0.59	$3.71 $3.34	$3.52 $3.19	71
RG393/U	50 10	0.390 0.094[7]	2	70 7.5	1,700	FEP	$18.91 $17.02	$17.96 $16.26	72
RG400/U	50 12.4	0.195 [19]	2	70 14.7	600 1,900	FEP	$8.31 $7.48	$7.89 $7.15	73
RG55B/U	53 3	0.202 0.032[1]	2	66 16.5	53	PE	$3.27 $2.94	$3.11 $2.81	74
RG58C/U	50 5	0.195 0.036[19]	1	66 20	44 1,900	PVC (NC) 0.98	$0.96 $0.86	$0.91 $0.83	75
RG58-P (1)	53 1	0.159 0.032[1]	1 45	70 17.3	143	FEP	$9.99 $8.99	$9.49 $8.59	76
RG58-TPX	50 6	0.190 0.035[1]	1	69	1,400	TPX 1.9	Call Call	Call Call	77
RG62A/U	93 1	0.239 0.025[1]	1 45	83 8.7	77	PVC	$2.73 $2.46	$2.59 $2.35	78
RG8A/U	50 1	0.405 0.085[7]	1	66 8	190	PVC (NC)	$3.86 $3.47	$3.67 $3.32	79
RG8X	50 1	0.242 0.056[19]	1	13.5	60 2,500	PVC (NC)	$4.64 $4.18	$4.41 $3.99	80
SEMIRIGID AND FORMABLE									
PECX001	50 115	0.013[1]	1	77 30	101	0.125	$14.93 $13.44	$14.18 $12.84	81
PECX002	50 115	0.013[1]	1	77 30	101	0.125	$17.68 $15.91	$16.80 $15.20	82
PECX003	50 72	0.02[1]	1	77 20	188	0.25	$21.08 $18.97	$20.03 $18.13	83

See Our Website For Current Pricing & Real-Time Stock Availability!

COAXIAL CABLES

Meets or Exceeds MIL-C-17 Specifications Where Applicable

MODEL NO.	COAX IMPEDANCE (Ohm) / MAXIMUM FREQUENCY (GHz.)	JACKET DIAMETER (in) / CONDUCTOR DIAM.(in) [strands]	NUMBER OF SHIELDS / RF SHIELDING (min dB)	VELOCITY FACTOR (%) / ATTENUATION AT 1 GHz. (dB/100 ft)	MAX. POWER HANDLING AT 1 GHz (W) / MAXIMUM OPERATING VOLTAGE (V RMS)	JACKET MATERIAL / MINIMUM BEND RADIUS (in)	PRICE PER FOOT 1-99 FT / 500-999 FT	PRICE PER FOOT 100-499 FT / 1000 + FT	ROW
SEMIRIGID AND FORMABLE									
PECX004	50 72	0.02[1]	1	77 20	188	0.25	$23.73 $21.36	$22.54 $20.41	84
PECX005	50 62	0.023[1]	1	77 17	314	0.25	$9.93 $8.94	$9.43 $8.54	85
PECX006	50 62	0.023[1]	1	77 17	231	0.25	$12.43 $11.19	$11.81 $10.69	86
PECX007	50 34	0.04[1]	1	77 10.5	580	0.5	$16.60 $14.94	$15.77 $14.28	87
PECX008	50 34	0.04[1]	1	77 10.5	580	0.5	$16.59 $14.93	$15.76 $14.27	88
PE-020SR (8)	50 27	0.004[1]	1	85	2.9		$24.12 $21.71	$22.91 $20.74	89
PE-034SR (2,8)	50 40	0.008[1]	1	60	10		$13.77 $12.39	$13.08 $11.84	90
PE-047SR (3,8)	50 40	0.011[1]	1	40	32		$12.39 $11.15	$11.77 $10.66	91
PE-047SR-STRAIGHT	50 40	0.047 0.011[1]	1	40		0.05	$13.36 $12.02	$12.69 $11.49	92
PE-118SR (2)	50 46	0.032[1]	1	12.5	500 3,000	0.4	$47.89 $43.10	$45.50 $41.19	93
PE-SR047AL (3,6)	50 20	0.011[1]	1 90	70 41	32		$11.40 $10.26	$10.83 $9.80	94
PE-SR047AL-STRAIGHT	50 20	0.047 0.011[1]	1 90	70 41	1,000	0.05	$12.52 $11.27	$11.89 $10.77	95
PE-SR047FL (12)	50 20	0.011[1]	1	70 36	32		$10.20 $9.18	$9.69 $8.77	96
PE-SR401AL-STRAIGHT	50 18	0.064	1	70 7.5	661		$25.17 $22.65	$23.91 $21.65	97
PE-SR401FL (11)	50 18	0.065[1]	1 100	70 6.8	279	0.75	$19.38 $17.44	$18.41 $16.67	98
PE-SR402-75 (3,8)	75 36	0.02[1]	1	12.5	280 3,500	0.1	$12.19 $10.97	$11.58 $10.48	99
PE-SR402-75-STRAIGHT	75 36	0.02[1]	1	12.5			$12.52 $11.27	$11.89 $10.77	1
PE-SR402AL (3,10)	50 36	0.036[1]	1	70 13	450		$11.40 $10.26	$10.83 $9.80	2
PE-SR402AL-STRAIGHT	50 36	0.141 0.036[1]	1	70 13		0.1	$11.57 $10.41	$10.99 $9.95	3
PE-SR402FL (4)	50 20	0.037[1]	110	70 12	400		$9.87 $8.88	$9.38 $8.49	4
PE-SR402FLJ (13)	50 34	0.161 0.036[1]	100	70 11.89	303.4 1,900	FEP 0.315	$10.42 $9.38	$9.90 $8.96	5
PE-SR402TN	50 36	0.036	1	70 12		1	$7.13 $6.42	$6.77 $6.13	6
PE-SR402TN-STRAIGHT	50 36	0.036	1	70 12		1	$9.81 $8.83	$9.32 $8.44	7
PE-SR405AL (3,9)	50 40	0.02[1]	1	23	130	0.05	$10.85 $9.77	$10.31 $9.33	8
PE-SR405AL-STRAIGHT	50 40	0.02[1]	1	23		0.05	$10.85 $9.77	$10.31 $9.33	9
PE-SR405FL (5)	50 20	0.02[1]	1	70 22.5	105		$13.47 $12.12	$12.80 $11.58	10
PE-SR405FLJ (14)	50 61	0.105 0.02[1]	1 100	70 19.5	121.5 1,500	FEP 0.5	$10.52 $9.47	$9.99 $9.05	11
PE-SR405TN	50 40	0.02[1]	1	22		0.05	$6.99 $6.29	$6.64 $6.01	12
PE-SR405TN-STRAIGHT	50 40	0.02[1]	1	22		0.05	$8.20 $7.38	$7.79 $7.05	13

See Our Website For Current Pricing & Real-Time Stock Availability!

COAXIAL CABLES

Meets or Exceeds MIL-C-17 Specifications Where Applicable

MODEL NO.	COAX IMPEDANCE (Ohm) MAXIMUM FREQUENCY (GHz.)	JACKET DIAMETER (in) CONDUCTOR DIAM.(in) [strands]	NUMBER OF SHIELDS RF SHIELDING (min dB)	VELOCITY FACTOR (%) ATTENUATION AT 1 GHz. (dB/100 ft)	MAX. POWER HANDLING AT 1 GHz (W) MAXIMUM OPERATING VOLTAGE (V RMS)	JACKET MATERIAL MINIMUM BEND RADIUS (in)	PRICE PER FOOT 1-99 FT 500-999 FT	PRICE PER FOOT 100-499 FT 1000 + FT	ROW
SEMIRIGID AND FORMABLE									
RG401/U (2,8)	50 20	 0.064[1]	1	70 7.5	1,400 3,000		$26.32 $23.69	$25.00 $22.64	14
RG402/U (3,8)	50 34	 0.036[1]	1	70 11.1	450		$8.67 $7.80	$8.24 $7.46	15
RG402/U-STRAIGHT	50 33	 0.036[1]	1	70 12	450		$9.44 $8.50	$8.97 $8.12	16
RG405/U (3,8)	50 40	 0.02[1]	1 -110	70 22	130		$9.10 $8.19	$8.65 $7.83	17
RG405/U-STRAIGHT	50 40	 0.02[1]	1 -110	70 22	130		$11.22 $10.10	$10.66 $9.65	18
SPF-250	50 5.8	0.303 0.075[1]	1	83		FRPE 1.25	$3.00 $3.00	$3.00 $3.00	19
SPF-375	50 6	0.435 0.11[1]	1	83		FRPE 1.75	$3.83 $3.83	$3.83 $3.83	20
SPF-500	50 6	0.545 0.14[1]	1	83		FRPE 2.25	$4.33 $4.33	$4.33 $4.33	21
SPO-250	50 5.8	0.303 0.075[1]	1	83		PE 1.25	$2.28 $2.28	$2.28 $2.28	22
SPO-375	50 6	0.430 0.11[1]	1	83		PE 1.75	$2.85 $2.85	$2.85 $2.85	23
SPO-500	50 6	0.530 0.14[1]	1	83		PE 2.25	$3.07 $3.07	$3.07 $3.07	24
SPP-250-LLPL	50 5.8	0.280 0.068[1]	1 100	76 5.5	650	FEP 1.25	$5.68 $5.68	$5.68 $5.68	25
SPP-375-LLPL	50 5.8	0.402 0.108[1]	1 100	76		FEP 1.25	$7.96 $7.96	$7.96 $7.96	26
SPP-500-LLPL	50 5.8	0.500 0.136[1]	1	76		FEP 1.5	$10.28 $10.28	$10.28 $10.28	27
TFT-402-LF	50 5.8	0.160 0.037[1]	2 80	76		FEP 0.75	$2.09 $1.88	$1.99 $1.80	28
TWINAX									
PE-S330 (TWINAX)	100 0.4	0.330 0.037[7]	2		300	PVC	$6.19 $5.57	$5.88 $5.32	29
RG108A/U (TWINAX)	78 1	0.235 0.038[7]	1	66 34.6	30	PVC	$3.14 $2.83	$2.98 $2.70	30

NOTES:

(1) P = PLENUM CABLE, NEC 725-2(b) CLASS 2 - REQUIRES SPECIAL CONNECTORS
(2) SEMI-RIGID CABLE, SOLD IN 5 FEET, STRAIGHT PIECES ONLY
(3) SEMI-RIGID CABLE, SOLD IN EITHER 5 FEET, STRAIGHT PIECES OR COILS OF 50 FEET
(4) RE-SHAPEABLE VERSION OF RG402/U
(5) RE-SHAPEABLE VERSION OF RG405/U
(6) TINNED ALUMINUM VERSION OF PE-047SR
(7) TINNED ALUMINUM VERSION OF RG401/U
(8) BARE COPPER JACKET
(9) TINNED ALUMINUM VERSION OF RG405/U
(10) TINNED ALUMINUM VERSION OF RG402/U
(11) RE-SHAPEABLE VERSION OF RG401/U
(12) RE-SHAPEABLE VERSION OF PE-047SR
(13) JACKETED RE-SHAPEABLE VERSION OF RG402/U
(14) JACKETED RE-SHAPEABLE VERSION OF RG405/U

MATERIALS:

Al (Tn)	TIN PLATED ALUMINUM
Cu	BARE COPPER
Cu (Tn)	TIN PLATED COPPER
FEP	FLUORINATED ETHYLENE PROPYLENE
LSZH	LOW SMOKE ZERO HALOGEN
PE	POLYETHYLENE
PTFE	POLYTETRAFLUOROETHYLENE
PTFE (FR)	FIBERGLASS REINFORCED PTFE
PVC	POLYVINYLCHLORIDE
PVC (NC)	NON-CONTAMINATED PVC
PVC (FR)	FIBERGLASS REINFORCED PVC

See Our Website For Current Pricing & Real-Time Stock Availability!

Connector Selection Guide

3 Easy Ways to Find your Product.....

1. Search by PE Part Number

If you know the PE part number you are searching for, please reference our Part Number Index on Page 395

2. Quick Reference Guide

(Page number refers to first appearance of product in the Connector Section)

Connector Series	Page
1.0/2.3	237
1.0mm	237
1.85mm	237
10-32	238
2.2-5	239
2.4mm	239
2.92mm	240
3.5mm	242
3/4”-20 Twinax	299
4.1/9.5 Mini DIN	242
4.3-10	242
7/16 DIN	243
75 Ohm 1.0/2.3	291
75 Ohm 1.6/5.6	291
75 Ohm BNC	291
75 Ohm F	293
75 Ohm MCX	294

Connector Series	Page
75 Ohm Mini SMB	294
75 Ohm N	295
75 Ohm RCA	296
75 Ohm SMB	296
75 Ohm SMC	297
75 Ohm TNC	298
Banana	300
BMA	245
BNC	247
BNC Twinax	299
C	251
D-Sub	252
Double Banana	300
FAKRA	252
FME	253
GR874	254

Connector Series	Page
HN	254
LC	255
MC-Card	255
MCX	255
MHV	257
Mini SMP	258
Mini UHF	258
MMBX	259
MMCX	259
N	260
NEX10	266
NMO Mount	266
QMA	266
QN	267
Rev. Pol. BNC	249
Rev. Pol. MCX	256

Connector Series	Page
Rev. Pol. N	265
Rev. Pol. SMA	274
Rev. Pol. TNC	288
Rev. Thread SMA	276
SC	267
SHV	268
SMA	269
SMB	277
SMC	279
SMP	280
SSMA	282
SSMB	284
SSMC	284
TNC	285
UHF	290
UMCX	290

Connectors

3. Connector Locator

Connector Type	Page
1.0/2.3 Jack Connectors	
Right Angle, Bulkhead, Cable Connectors	237
Right Angle, PCB Mount	237
Straight, Bulkhead, Cable Connectors	237
Straight, Bulkhead, PCB Mount	237
Straight, PCB Mount	237
1.0/2.3 Plug Connectors	
Right Angle, Cable Connectors	237
Straight, Cable Connectors	237
1.0mm Female Connectors	
Straight, PCB Mount	237
1.85mm Female Connectors	
Straight, 2 Hole Flange, Field Replaceable Contact	238
Straight, 4 Hole Flange, Field Replaceable Contact	238
Straight, Bulkhead, Cable Connectors	238
Straight, Cable Connectors	238
Straight, PCB Mount	238
1.85mm Male Connectors	
Straight, Cable Connectors	237
Straight, PCB Mount	238
Straight, Threaded, Field Replaceable Contact	238
10-32 Female Connectors	
Right Angle, PCB Mount	239
Straight, Bulkhead, Cable Connectors	239

Connector Type	Page
Straight, Bulkhead, Terminal	239
Straight, Cable Connectors	238
Straight, PCB Mount	238
10-32 Male Connectors	
Right Angle, Cable Connectors	238
Straight, Cable Connectors	238
2.2-5 Female Connectors	
Straight, Bulkhead, Cable Connectors	239
Straight, Cable Connectors	239
2.2-5 Male Connectors	
Right Angle, Cable Connectors	239
Straight, Cable Connectors	239
2.4mm Female Connectors	
Straight, 2 Hole Flange, Field Replaceable Contact	240
Straight, 4 Hole Flange, Field Replaceable Contact	240
Straight, Bulkhead, Cable Connectors	240
Straight, Cable Connectors	240
Straight, PCB Mount	240
2.4mm Male Connectors	
Straight, 2 Hole Flange, Terminal	240
Straight, Cable Connectors	239
Straight, PCB Mount	239
2.92mm Female Connectors	
Straight, 2 Hole Flange, Field Replaceable Contact	241

Connector Locator

Connector Type	Page
Straight, 4 Hole Flange, Cable Connectors	241
Straight, 4 Hole Flange, Field Replaceable Contact	241
Straight, Bulkhead, Cable Connectors	241
Straight, Cable Connectors	241
Straight, PCB Mount	241
2.92mm Male Connectors	
Straight, 2 Hole Flange, Field Replaceable Contact	241
Straight, Cable Connectors	240
Straight, PCB Mount	241
3.5mm Female Connectors	
Straight, Bulkhead, Cable Connectors	242
Straight, Cable Connectors	242
3.5mm Male Connectors	
Straight, Cable Connectors	242
4.1/9.5 Mini DIN Female Connectors	
Straight, Bulkhead, Cable Connectors	242
Straight, Cable Connectors	242
4.1/9.5 Mini DIN Male Connectors	
Right Angle, Cable Connectors	242
Straight, Cable Connectors	242
4.3-10 Female Connectors	
Straight, 4 Hole Flange, Cable Connectors	243
Straight, 4 Hole Flange, Terminal	243
Straight, Bulkhead, Cable Connectors	243
Straight, Cable Connectors	243
4.3-10 Male Connectors	
Right Angle, Cable Connectors	243
Straight, Cable Connectors	242
7/16 DIN Female Connectors	
Straight, 4 Hole Flange, Cable Connectors	245
Straight, 4 Hole Flange, Terminal	245
Straight, Bulkhead, Cable Connectors	245
Straight, Bulkhead, Terminal	245
Straight, Cable Connectors	244
7/16 DIN Male Connectors	
Right Angle, Cable Connectors	244
Straight, Cable Connectors	244
75 Ohm 1.0/2.3 Jack Connectors	
Right Angle, Bulkhead, PCB Mount	291
Straight, Bulkhead, PCB Mount	291
75 Ohm 1.0/2.3 Plug Connectors	
Straight, Cable Connectors	291
75 Ohm 1.6/5.6 Jack Connectors	
Right Angle, Bulkhead, Cable Connectors	291
Right Angle, PCB Mount	291
Straight, Bulkhead, PCB Mount	291
75 Ohm 1.6/5.6 Plug Connectors	
Right Angle, Cable Connectors	291
Straight, Cable Connectors	291
75 Ohm BNC Female Connectors	
Right Angle, 4 Hole Flange, Terminal	293
Right Angle, Bulkhead, Terminal	293
Straight, 4 Hole Flange, Cable Connectors	292

Connector Type	Page
Straight, 4 Hole Flange, Terminal	293
Straight, Bulkhead, Cable Connectors	292
Straight, Bulkhead, PCB Mount	292
Straight, Bulkhead, Terminal	292
Straight, Cable Connectors	292
Straight, PCB Mount	292
75 Ohm BNC Male Connectors	
Right Angle, Cable Connectors	292
Straight, 4 Hole Flange, Terminal	292
Straight, Bulkhead, Terminal	292
Straight, Cable Connectors	291
75 Ohm F Female Connectors	
Right Angle, Bulkhead, PCB Mount	294
Right Angle, PCB Mount	294
Straight, 4 Hole Flange, Terminal	294
Straight, Bulkhead, Cable Connectors	293
Straight, Bulkhead, PCB Mount	294
Straight, Bulkhead, Terminal	294
Straight, PCB Mount	293
Straight, Thread-In, Terminal	294
75 Ohm F Male Connectors	
Right Angle, Cable Connectors	293
Straight, Cable Connectors	293
75 Ohm MCX Jack Connectors	
Right Angle, PCB Mount	294
Straight, Cable Connectors	294
Straight, PCB Mount	294
75 Ohm MCX Plug Connectors	
Right Angle, Cable Connectors	294
Straight, Cable Connectors	294
75 Ohm Mini SMB Jack Connectors	
Right Angle, Bulkhead, PCB Mount	295
Right Angle, PCB Mount	295
Straight, 2 Hole Flange, Terminal	295
Straight, Cable Connectors	295
Straight, PCB Mount	295
75 Ohm Mini SMB Plug Connectors	
Right Angle, Cable Connectors	295
Straight, Cable Connectors	294
75 Ohm N Female Connectors	
Straight, 4 Hole Flange, Terminal	296
Straight, Bulkhead, Terminal	296
Straight, Cable Connectors	295
75 Ohm N Male Connectors	
Right Angle, Cable Connectors	295
Straight, 4 Hole Flange, Terminal	295
Straight, Cable Connectors	295
75 Ohm RCA Female Connectors	
Straight, Bulkhead, Cable Connectors	296
75 Ohm RCA Male Connectors	
Right Angle, Cable Connectors	296
Straight, Cable Connectors	296
75 Ohm SMB Jack Connectors	

Connector Locator

Connector Type	Page
Right Angle, PCB Mount	297
Straight, Bulkhead, Cable Connectors	297
Straight, Bulkhead, Terminal	297
Straight, Cable Connectors	297
Straight, PCB Mount	297
75 Ohm SMB Plug Connectors	
Right Angle, Cable Connectors	296
Straight, Bulkhead, Terminal	296
Straight, Cable Connectors	296
Straight, PCB Mount	296
75 Ohm SMC Jack Connectors	
Right Angle, PCB Mount	298
Straight, Bulkhead, Cable Connectors	298
Straight, Bulkhead, Terminal	298
Straight, Cable Connectors	298
Straight, PCB Mount	298
75 Ohm SMC Plug Connectors	
Right Angle, Cable Connectors	298
Right Angle, PCB Mount	298
Straight, Bulkhead, Terminal	297
Straight, Cable Connectors	297
75 Ohm TNC Female Connectors	
Straight, 4 Hole Flange, Terminal	299
Straight, Bulkhead, Cable Connectors	298
Straight, Bulkhead, Terminal	298
75 Ohm TNC Male Connectors	
Right Angle, Cable Connectors	298
Straight, Cable Connectors	298
78 Ohm BNC Twinax Jack Connectors	
Right Angle, PCB Mount	299
Straight, 4 Hole Flange, Terminal	299
Straight, Bulkhead, Cable Connectors	299
Straight, Bulkhead, Terminal	299
Straight, Cable Connectors	299
Straight, PCB Mount	299
78 Ohm BNC Twinax Plug Connectors	
Straight, Cable Connectors	299
95 Ohm 3/4”-20 Twinax Female Connectors	
Straight, 4 Hole Flange, Terminal	300
Straight, Bulkhead, Terminal	300
Straight, Cable Connectors	299
95 Ohm 3/4”-20 Twinax Male Connectors	
Straight, Cable Connectors	299
Banana Plug Connectors	
Straight, Cable Connectors	300
BMA Jack Connectors	
Right Angle, 2 Hole Flange, Cable Connectors	247
Straight, 2 Hole Flange, Cable Connectors	246
Straight, 2 Hole Flange, Terminal	246
Straight, 4 Hole Flange, Terminal	246
Straight, Bulkhead, Cable Connectors	246
Straight, Cable Connectors	246
Straight, PCB Mount	246

Connector Type	Page
Straight, Terminal	246
Straight, Thread-In, Terminal	247
BMA Plug Connectors	
Right Angle, PCB Mount	246
Straight, 2 Hole Flange, Field Replaceable Contact	245
Straight, 2 Hole Flange, Terminal	246
Straight, 4 Hole Flange, Terminal	246
Straight, Bulkhead, Cable Connectors	245
Straight, PCB Mount	245
Straight, Thread-In, Terminal	246
BNC Female Connectors	
Right Angle, 4 Hole Flange, Terminal	249
Right Angle, Bulkhead, Terminal	249
Straight, 4 Hole Flange, Cable Connectors	249
Straight, 4 Hole Flange, Terminal	249
Straight, Bulkhead, Cable Connectors	249
Straight, Bulkhead, PCB Mount	249
Straight, Bulkhead, Terminal	249
Straight, Cable Connectors	248
Straight, PCB Mount	248
BNC Male Connectors	
Right Angle, Cable Connectors	248
Straight, 4 Hole Flange, Terminal	248
Straight, Bulkhead, Terminal	248
Straight, Cable Connectors	247
C Female Connectors	
Straight, 4 Hole Flange, Cable Connectors	251
Straight, 4 Hole Flange, Terminal	251
Straight, Bulkhead, Cable Connectors	251
Straight, Bulkhead, Terminal	251
Straight, Cable Connectors	251
C Male Connectors	
Right Angle, Cable Connectors	251
Straight, 4 Hole Flange, Terminal	251
Straight, Cable Connectors	251
Double Banana Plug Connectors	
Straight, Cable Connectors	300
D-Sub Plug Connectors	
Right Angle, Cable Connectors	252
Straight, Cable Connectors	252
D-Sub Receptacle Connectors	
Right Angle, Cable Connectors	252
Straight, Cable Connectors	252
FAKRA Jack Connectors	
Right Angle, Cable Connectors	253
Right Angle, PCB Mount	253
Straight, Cable Connectors	253
FAKRA Plug Connectors	
Right Angle, PCB Mount	253
Straight, Cable Connectors	252
Straight, PCB Mount	252
FME Jack Connectors	
Straight, Cable Connectors	254

Connector Locator

Connector Type	Page
FME Plug Connectors	
Straight, Bulkhead, Terminal	253
Straight, Cable Connectors	253
GR874 Sexless Connectors	
Straight, Cable Connectors	254
HN Female Connectors	
Straight, 4 Hole Flange, Terminal	254
Straight, Bulkhead, Terminal	254
Straight, Cable Connectors	254
HN Male Connectors	
Right Angle, Cable Connectors	254
Straight, Cable Connectors	254
LC Female Connectors	
Straight, 4 Hole Flange, Terminal	255
Straight, Cable Connectors	255
LC Male Connectors	
Right Angle, Cable Connectors	255
Straight, Cable Connectors	255
MC-Card Plug Connectors	
Right Angle, Cable Connectors	255
Straight, Cable Connectors	255
MCX Jack Connectors	
Right Angle, Bulkhead, Terminal	256
Right Angle, PCB Mount	256
Straight, 2 Hole Flange, Terminal	256
Straight, Bulkhead, Cable Connectors	256
Straight, Bulkhead, Terminal	256
Straight, Cable Connectors	256
Straight, PCB Mount	256
MCX Plug Connectors	
Right Angle, Cable Connectors	255
Right Angle, PCB Mount	256
Straight, Cable Connectors	255
Straight, PCB Mount	255
MHV Female Connectors	
Straight, 4 Hole Flange, Cable Connectors	258
Straight, 4 Hole Flange, Terminal	258
Straight, Bulkhead, Cable Connectors	257
Straight, Bulkhead, Terminal	257
Straight, Cable Connectors	257
MHV Male Connectors	
Right Angle, Cable Connectors	257
Straight, Cable Connectors	257
Mini SMP Female Connectors	
Right Angle, Cable Connectors	258
Straight, Cable Connectors	258
Mini SMP Male Connectors	
Right Angle, PCB Mount	258
Straight, PCB Mount	258
Straight, Solder, Terminal	258
Mini UHF Female Connectors	
Straight, 4 Hole Flange, Terminal	259
Straight, Bulkhead, Cable Connectors	258

Connector Type	Page
Straight, Bulkhead, PCB Mount	259
Straight, Bulkhead, Terminal	259
Straight, Cable Connectors	258
Mini UHF Male Connectors	
Straight, Cable Connectors	258
MMBX Jack Connectors	
Straight, PCB Mount	259
Straight, Thread-In, Terminal	259
MMBX Plug Connectors	
Right Angle, Cable Connectors	259
Straight, Cable Connectors	259
Straight, PCB Mount	259
MMCX Jack Connectors	
Right Angle, PCB Mount	260
Straight, Cable Connectors	260
Straight, PCB Mount	260
MMCX Plug Connectors	
Right Angle, Cable Connectors	260
Straight, Cable Connectors	259
Straight, PCB Mount	260
N Female Connectors	
Right Angle, 4 Hole Flange, Terminal	265
Right Angle, Bulkhead, PCB Mount	265
Straight, 2 Hole Flange, Terminal	264
Straight, 4 Hole Flange, Cable Connectors	264
Straight, 4 Hole Flange, Terminal	265
Straight, Bulkhead, Cable Connectors	263
Straight, Bulkhead, PCB Mount	264
Straight, Bulkhead, Terminal	264
Straight, Cable Connectors	262
Straight, PCB Mount	263
Straight, Press-In, Terminal	265
N Male Connectors	
Right Angle, Cable Connectors	262
Straight, 4 Hole Flange, Terminal	262
Straight, Bulkhead, Terminal	261
Straight, Cable Connectors	260
NEX10 Female Connectors	
Straight, Bulkhead, Cable Connectors	266
Straight, Cable Connectors	266
NEX10 Male Connectors	
Right Angle, Cable Connectors	266
Straight, Cable Connectors	266
NMO Mount Sexless Connectors	
Straight, Cable Connectors	266
QMA Female Connectors	
Right Angle, PCB Mount	267
Straight, Bulkhead, Cable Connectors	267
Straight, Cable Connectors	267
Straight, PCB Mount	267
QMA Male Connectors	
Right Angle, Cable Connectors	266
Straight, Cable Connectors	266

Connector Locator

Connector Type	Page
QN Female Connectors	
Straight, 4 Hole Flange, Terminal	267
Straight, Bulkhead, Cable Connectors	267
QN Male Connectors	
Right Angle, Cable Connectors	267
Straight, Cable Connectors	267
Reverse Polarity BNC Female Connectors	
Right Angle, Bulkhead, Terminal	250
Straight, 4 Hole Flange, Terminal	250
Straight, Bulkhead, Cable Connectors	250
Straight, Bulkhead, Terminal	250
Straight, Cable Connectors	250
Reverse Polarity BNC Male Connectors	
Right Angle, Cable Connectors	250
Straight, 4 Hole Flange, Terminal	250
Straight, Cable Connectors	249
Reverse Polarity MCX Jack Connectors	
Right Angle, Bulkhead, PCB Mount	257
Straight, Bulkhead, Cable Connectors	257
Straight, Bulkhead, PCB Mount	257
Reverse Polarity MCX Plug Connectors	
Right Angle, Cable Connectors	256
Straight, Cable Connectors	256
Reverse Polarity N Female Connectors	
Straight, Cable Connectors	265
Reverse Polarity N Male Connectors	
Straight, Cable Connectors	265
Reverse Polarity SMA Female Connectors	
Right Angle, Bulkhead, PCB Mount	276
Right Angle, PCB Mount	276
Straight, 2 Hole Flange, Terminal	276
Straight, 4 Hole Flange, Terminal	276
Straight, Bulkhead, Cable Connectors	275
Straight, Bulkhead, PCB Mount	276
Straight, Bulkhead, Terminal	276
Straight, Cable Connectors	275
Straight, PCB Mount	275
Reverse Polarity SMA Male Connectors	
Right Angle, Cable Connectors	275
Straight, Cable Connectors	275
Reverse Polarity TNC Female Connectors	
Straight, 4 Hole Flange, Terminal	289
Straight, Bulkhead, Cable Connectors	289
Straight, Bulkhead, Terminal	289
Straight, Cable Connectors	289
Reverse Polarity TNC Male Connectors	
Right Angle, Cable Connectors	289
Straight, 4 Hole Flange, Terminal	289
Straight, Cable Connectors	288
Reverse Thread SMA Female Connectors	
Right Angle, PCB Mount	277
Straight, 4 Hole Flange, Terminal	277
Straight, Bulkhead, Cable Connectors	277
Straight, Cable Connectors	276
Straight, PCB Mount	277
Reverse Thread SMA Male Connectors	
Right Angle, Cable Connectors	276
Straight, Cable Connectors	276
SC Female Connectors	
Straight, 4 Hole Flange, Terminal	268
Straight, Bulkhead, Terminal	268
SC Male Connectors	
Right Angle, Cable Connectors	268
Straight, Cable Connectors	267
SHV Jack Connectors	
Straight, 4 Hole Flange, Terminal	268
Straight, Bulkhead, Cable Connectors	268
Straight, Bulkhead, Terminal	268
SHV Plug Connectors	
Straight, Bulkhead, Terminal	268
Straight, Cable Connectors	268
SMA Female Connectors	
Right Angle, 2 Hole Flange, Terminal	274
Right Angle, 4 Hole Flange, Field Replaceable Contact	274
Right Angle, 4 Hole Flange, Terminal	274
Right Angle, Bulkhead, PCB Mount	274
Right Angle, Bulkhead, Terminal	274
Right Angle, PCB Mount	274
Straight, 2 Hole Flange, Cable Connectors	273
Straight, 2 Hole Flange, Field Replaceable Contact	273
Straight, 2 Hole Flange, Terminal	273
Straight, 4 Hole Flange, Cable Connectors	273
Straight, 4 Hole Flange, Field Replaceable Contact	273
Straight, 4 Hole Flange, Terminal	274
Straight, Bulkhead, Cable Connectors	272
Straight, Bulkhead, PCB Mount	272
Straight, Bulkhead, Terminal	272
Straight, Cable Connectors	271
Straight, PCB Mount	271
Straight, Press-In, Terminal	274
SMA Male Connectors	
Right Angle, Cable Connectors	270
Straight, 2 Hole Flange, Field Replaceable Contact	270
Straight, 2 Hole Flange, Terminal	270
Straight, 4 Hole Flange, Field Replaceable Contact	270
Straight, 4 Hole Flange, Terminal	270
Straight, Bulkhead, Terminal	270
Straight, Cable Connectors	269
Straight, PCB Mount	269
SMB Jack Connectors	
Right Angle, Bulkhead, PCB Mount	279
Right Angle, Bulkhead, Terminal	279
Right Angle, PCB Mount	278
Straight, 2 Hole Flange, Terminal	278
Straight, 4 Hole Flange, Terminal	278
Straight, Bulkhead, Cable Connectors	278

Connector Locator

Connector Type	Page
Straight, Bulkhead, PCB Mount	278
Straight, Bulkhead, Terminal	278
Straight, Cable Connectors	278
Straight, PCB Mount	278
SMB Plug Connectors	
Right Angle, Cable Connectors	278
Right Angle, PCB Mount	278
Straight, Bulkhead, Terminal	277
Straight, Cable Connectors	277
Straight, PCB Mount	277
SMC Jack Connectors	
Right Angle, Bulkhead, Terminal	280
Right Angle, PCB Mount	280
Straight, 4 Hole Flange, Terminal	280
Straight, Bulkhead, Cable Connectors	279
Straight, Bulkhead, PCB Mount	280
Straight, Bulkhead, Terminal	280
Straight, Cable Connectors	279
Straight, PCB Mount	279
SMC Plug Connectors	
Right Angle, Cable Connectors	279
Right Angle, PCB Mount	279
Straight, Cable Connectors	279
Straight, PCB Mount	279
SMP Female Connectors	
Right Angle, Cable Connectors	282
Straight, Cable Connectors	282
Straight, PCB Mount	282
SMP Male Connectors	
Right Angle, PCB Mount	281
Straight, 2 Hole Flange, Cable Connectors	281
Straight, 2 Hole Flange, Shroud	281
Straight, 2 Hole Flange, Terminal	281
Straight, Bulkhead, Cable Connectors	281
Straight, PCB Mount	280
Straight, Solder, Shroud	281
Straight, Solder, Terminal	281
Straight, Terminal	281
Straight, Thread-In, Shroud	281
Straight, Thread-In, Terminal	281
SSMA Female Connectors	
Right Angle, PCB Mount	283
Straight, 2 Hole Flange, Cable Connectors	283
Straight, 2 Hole Flange, Terminal	283
Straight, 4 Hole Flange, Cable Connectors	283
Straight, 4 Hole Flange, Terminal	283
Straight, Bulkhead, Cable Connectors	283
Straight, Bulkhead, PCB Mount	283
Straight, Bulkhead, Terminal	283
Straight, Cable Connectors	283
Straight, PCB Mount	283
SSMA Male Connectors	
Right Angle, Cable Connectors	282
Straight, 4 Hole Flange, Terminal	282
Straight, Cable Connectors	282
Straight, PCB Mount	282
SSMB Jack Connectors	
Right Angle, PCB Mount	284
Straight, 4 Hole Flange, Terminal	284
Straight, Bulkhead, Cable Connectors	284
Straight, Bulkhead, Terminal	284
Straight, Cable Connectors	284
Straight, PCB Mount	284
SSMB Plug Connectors	
Right Angle, Cable Connectors	284
Straight, Cable Connectors	284
SSMC Jack Connectors	
Right Angle, Bulkhead, Cable Connectors	285
Right Angle, Bulkhead, PCB Mount	285
Right Angle, Bulkhead, Terminal	285
Right Angle, PCB Mount	285
Straight, 2 Hole Flange, Terminal	285
Straight, 4 Hole Flange, Terminal	285
Straight, Bulkhead, Cable Connectors	285
Straight, Bulkhead, Terminal	285
Straight, PCB Mount	285
SSMC Plug Connectors	
Right Angle, Cable Connectors	284
Right Angle, PCB Mount	284
Straight, Cable Connectors	284
TNC Female Connectors	
Right Angle, Bulkhead, Cable Connectors	288
Right Angle, Bulkhead, PCB Mount	288
Right Angle, Bulkhead, Terminal	288
Right Angle, PCB Mount	288
Straight, 4 Hole Flange, Cable Connectors	288
Straight, 4 Hole Flange, Terminal	288
Straight, Bulkhead, Cable Connectors	287
Straight, Bulkhead, PCB Mount	287
Straight, Bulkhead, Terminal	288
Straight, Cable Connectors	287
TNC Male Connectors	
Right Angle, Cable Connectors	286
Straight, 4 Hole Flange, Terminal	286
Straight, Cable Connectors	285
TNC Sexless Connectors	
Straight, Cable Connectors	285
UHF Female Connectors	
Straight, 4 Hole Flange, Terminal	290
Straight, Bulkhead, Terminal	290
Straight, Cable Connectors	290
UHF Male Connectors	
Straight, Cable Connectors	290
UHF Sexless Connectors	
Straight, Cable Connectors	290
UMCX Jack Connectors	
Straight, PCB Mount	290

1.0mm Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1	2-4	5-9	10 +	ROW
	Female								
PCB Mount		Clamp/Solder (Captive Contact)	End Launch	PE45403	$1,166.08	$1,125.27	$1,084.45	$1,049.47	1

1.0/2.3 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE44244	$16.44	$15.62	$14.80	$14.14	2
			RG188-DS, RG316-DS	PE45166	$12.97	$12.32	$11.67	$11.15	3
			RG55, RG142, RG223, RG400	PE44242	$14.76	$14.02	$13.28	$12.69	4
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE44243	$16.97	$16.12	$15.27	$14.59	5
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE44249	$16.47	$15.65	$14.82	$14.16	6
			RG316-DS, RG188-DS	PE44783	$18.08	$17.18	$16.27	$15.55	7
			RG55, RG142, RG223, RG400	PE44247	$17.16	$16.30	$15.44	$14.76	8
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE44248	$18.92	$17.97	$17.03	$16.27	9
	Jack								
PCB Mount		Solder	Thru Hole with .200 inch x .055 inch Hole Spacing	PE44257	$11.76	$11.17	$10.58	$10.11	10
	Jack, Bulkhead Mount								
Cable Connectors		Crimp/Solder	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100A-FR, PE-C100, PE-B100 with .217 inch DD Hole	PE44254	$18.80	$17.86	$16.92	$16.17	11
		Solder/Solder	PE-SR405AL, PE-SR405FL, RG405 with .235 inch D Hole	PE44256	$20.81	$19.77	$18.73	$17.90	12
PCB Mount		Solder	Thru Hole with .220 inch Diameter	PE44259	$14.52	$13.79	$13.07	$12.49	13
	Jack Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .055 inch Hole Spacing	PE44258	$14.81	$14.07	$13.33	$12.74	14
	Jack Right Angle, Bulkhead Mount								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188 with .236 inch DD Hole	PE44261	$17.63	$16.75	$15.87	$15.16	15
			RG58 with .236 inch DD Hole	PE44260	$17.97	$17.07	$16.17	$15.45	16

1.85mm Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	See Web for Volume Pricing			ROW
	Male								
Cable Connectors		Clamp/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44799	$131.93	See Web for Volume Pricing			17
			PE-P086, PE-P086LL	PE45005	$96.63				18
		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE45410	$98.30				19
			PECX001, PECX002	PE45482	$120.89				20
			PECX003, PECX004	PE45484	$120.89				21
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44336	$163.48				22
			PE-SR405AL, RG405, PE-SR405FLJ	PE45413	$102.13				23

*** Fits MIL-C-17 and equivalent cable versions only**

Connectors

See Our Website For Current Pricing & Real-Time Stock Availability!

1.85mm Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	PRICE See Web for Volume Pricing			ROW
PCB Mount		Clamp/Solder (Captive Contact)	End Launch	PE45517	$313.68				24
			End Launch	PE45518	$296.12				25
	Male, Threaded Mount								
Field Replaceable		Field Replaceable	.009 inch Pin	PE44338	$171.11				26
	Female								
Cable Connectors		Clamp/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44800	$148.98	See Web for Volume Pricing			27
PCB Mount		Clamp/Solder (Captive Contact)	End Launch	PE45515	$275.77				28
			End Launch	PE45402	$256.13				29
			End Launch	PE45477	$187.58				30
			End Launch	PE45516	$274.10				31
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405 with .252 inch D Hole	PE44802	$141.00				32
	Female, 2 Hole Flange Mount								
Field Replaceable		Field Replaceable	0.009 inch Pin	PE45632	$81.03				33
			0.009 inch Pin	PE45633	$77.14				34
	Female, 4 Hole Flange Mount								
Field Replaceable		Field Replaceable	0.009 inch Pin	PE45631	$60.60				35
			0.009 inch Pin with .340 inch Hole Spacing	PE45630	$65.09				36

10-32 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	PRICE 25-49	PRICE 50-99	PRICE 100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE44353	$38.30	$36.39	$34.47	$32.94	37
			RG178, RG196	PE44354	$45.12	$43.32	$41.96	$41.06	38
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE44351	$27.36	$25.99	$24.62	$23.53	39
			RG178, RG196	PE44352	$41.52	$39.44	$37.37	$35.71	40
			RG188-DS, RG316-DS	PE45170	$26.82	$25.48	$24.14	$23.07	41
	Male Right Angle								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE44355	$27.63	$26.25	$24.87	$23.76	42
			RG178, RG196	PE44356	$45.58	$43.30	$41.02	$39.20	43
			RG316-DS, RG188-DS	PE45032	$27.91	$26.51	$25.12	$24.00	44
	Female								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE44363	$45.85	$43.56	$41.27	$39.43	45
			RG178, RG196	PE44364	$38.65	$36.72	$34.79	$33.24	46
		Crimp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE44361	$36.90	$35.06	$33.21	$31.73	47
			RG178, RG196	PE44362	$35.09	$33.69	$32.63	$31.93	48
			RG188-DS, RG316-DS	PE45171	$27.73	$26.34	$24.96	$23.85	49
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE44359	$27.78	$26.39	$25.00	$23.89	50

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

10-32 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100A-FR, PE-C100, PE-B100 with .295 inch D Hole	PE44367	$34.83	$33.09	$31.35	$29.95	51
			RG178, RG196 with .295 inch D Hole	PE44368	$40.23	$38.22	$36.21	$34.60	52
		Crimp/Solder	RG174, RG316, RG188 with .295 inch D Hole	PE44365	$37.62	$35.74	$33.86	$32.35	53
			RG178, RG196 with .295 inch D Hole	PE44366	$36.35	$34.53	$32.72	$31.26	54
Terminal		Solder	Solder Cup with .177 inch D Hole	PE44357	$29.51	$28.03	$26.56	$25.38	55
			Solder Cup with .295 inch D Hole	PE44358	$38.65	$36.72	$34.79	$33.24	56
	Female Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE44360	$33.97	$32.27	$30.57	$29.21	57

2.2-5 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45673	$18.48	$17.56	$16.63	$15.89	58
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45677	$24.08	$22.88	$21.67	$20.71	59
			TFT-402, TFT-402-LF	TC-402-225M-LP	$25.30	$25.30	$25.30	$25.30	60
	Male Right Angle								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45674	$25.20	$23.94	$22.68	$21.67	61
	Female								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45675	$18.48	$17.56	$16.63	$15.89	62
			TFT-402, TFT-402-LF	TC-402-225F-LP	$25.30	$25.30	$25.30	$25.30	63
	Female, Bulkhead Mount								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45676	$21.28	$20.22	$19.15	$18.30	64

2.4mm Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	See Web for Volume Pricing			ROW
	Male								
Cable Connectors		Clamp/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE45541	$97.71	See Web for Volume Pricing			65
		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE45411	$93.62				66
			PE-SR405AL, PE-SR405FL, RG405	PE44215	$100.05				67
			PE-SR405AL, RG405, PE-SR405FLJ	PE45414	$93.62				68
PCB Mount		Clamp	Vertical Launch	PE45457	$52.89				69
			Vertical Launch	PE45456	$51.90				70
		Clamp/Solder (Captive Contact)	End Launch	PE45514	$186.76				71
			End Launch	PE45513	$229.32				72

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

2.4mm Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	PRICE See Web for Volume Pricing			ROW
	Male, 2 Hole Flange Mount								
Terminal		Solder	Pin with .481 inch Hole Spacing	PE44220	$174.91				73
	Female								
Cable Connectors		Clamp/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44216	$205.60		See Web for Volume Pricing		74
PCB Mount		Clamp	Vertical Launch	PE45455	$49.44				75
			Vertical Launch	PE45454	$49.44				76
		Clamp/Solder (Captive Contact)	End Launch	PE45511	$206.99				77
			End Launch	PE45512	$230.89				78
			End Launch	PE45473	$100.13				79
			End Launch	PE45472	$104.04				80
			End Launch	PE45476	$104.04				81
			End Launch	PE45401	$190.77				82
			End Launch	PE45474	$98.26				83
			End Launch	PE45475	$98.26				84
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405 with .252 inch D Hole	PE44801	$149.71				85
	Female, 2 Hole Flange Mount								
Field Replaceable		Field Replaceable	0.009 inch Pin	PE45626	$65.77		See Web for Volume Pricing		86
			0.009 inch Pin	PE45622	$60.92				87
			0.009 inch Pin with .481 inch Hole Spacing	PE45618	$50.61				88
			0.012 inch Pin	PE45623	$49.20				89
			0.012 inch Pin	PE45627	$53.10				90
			0.012 inch Pin with .481 inch Hole Spacing	PE45619	$49.26				91
			0.015 inch Pin	PE45624	$51.65				92
			0.015 inch Pin	PE45628	$55.24				93
			0.015 inch Pin with .481 inch Hole Spacing	PE45620	$51.73				94
			0.02 inch Pin	PE45625	$54.11				95
			0.02 inch Pin	PE45629	$57.87				96
			0.02 inch Pin with .481 inch Hole Spacing	PE45621	$54.19				97
	Female, 4 Hole Flange Mount								
Field Replaceable		Field Replaceable	0.009 inch Pin	PE45614	$53.25				98
			0.009 inch Pin with .340 inch Hole Spacing	PE45610	$58.03				99
			0.012 inch Pin	PE45615	$42.60				1
			0.012 inch Pin with .340 inch Hole Spacing	PE45611	$53.83				2
			0.015 inch Pin	PE45616	$44.74				3
			0.015 inch Pin with .340 inch Hole Spacing	PE45612	$49.21				4
			0.02 inch Pin	PE45617	$46.85				5
			0.02 inch Pin with .340 inch Hole Spacing	PE45613	$44.99				6

2.92mm Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	PRICE See Web for Volume Pricing			ROW
	Male								
Cable Connectors		Clamp/Solder	PE-SR047FL, PE-SR047AL, PE-047SR	PE44797	$120.42		See Web for Volume Pricing		7
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44796	$88.35				8
		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE45412	$85.12				9
			PE-118SR, 0.118 inch	PE45486	$119.14				10
			PE-120SRLL, Tinned 120LL	PE45487	$112.97				11
			PECX001, PECX002	PE45483	$112.97				12
			PECX005, PECX006	PE45485	$114.66				13
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE4987	$51.35				14
			PE-SR405AL, PE-SR405FL, RG405	PE4988	$54.17				15
			PE-SR405AL, RG405, PE-SR405FLJ	PE45415	$85.12				16

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

2.92mm Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	PRICE See Web for Volume Pricing			ROW
PCB Mount		Clamp	Vertical Launch	PE45453	$49.29	See Web for Volume Pricing			17
			Vertical Launch	PE45452	$49.29				18
		Clamp/Solder (Captive Contact)	End Launch	PE45509	$200.97				19
			End Launch	PE45510	$189.56				20
	Male, 2 Hole Flange Mount								
Field Replaceable		Field Replaceable	.012 inch Pin with .481 inch Hole Spacing	PE44232	$77.38				21
	Female								
Cable Connectors		Clamp/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44798	$134.88	See Web for Volume Pricing			22
			PE-SR402AL, PE-SR402FL, RG402	PE44227	$136.09				23
PCB Mount		Clamp	Vertical Launch	PE45450	$46.06				24
			Vertical Launch	PE45451	$46.06				25
		Clamp/Solder (Captive Contact)	End Launch	PE45508	$172.57				26
			End Launch	PE45507	$182.92				27
			End Launch	PE45470	$77.01				28
			End Launch	PE45400	$180.09				29
			End Launch	PE45467	$77.01				30
			End Launch	PE45468	$77.01				31
			End Launch	PE45469	$77.01				32
			End Launch	PE45471	$72.73				33
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405 with .235 inch D Hole	PE4992	$174.91				34
	Female, 2 Hole Flange Mount								
Field Replaceable		Field Replaceable	0.009 inch Pin	PE45602	$44.59	See Web for Volume Pricing			35
			0.009 inch Pin	PE45606	$44.59				36
			0.009 inch Pin with .481 inch Hole Spacing	PE45598	$47.27				37
			0.012 inch Pin	PE45603	$35.67				38
			0.012 inch Pin	PE45607	$35.67				39
			.012 inch Pin with .481 inch Hole Spacing	PE44229	$144.37				40
			0.012 inch Pin with .481 inch Hole Spacing	PE45599	$39.68				41
			0.015 inch Pin	PE45604	$37.46				42
			0.015 inch Pin	PE45608	$37.46				43
			0.015 inch Pin with .481 inch Hole Spacing	PE45600	$41.66				44
			0.02 inch Pin	PE45605	$39.24				45
			0.02 inch Pin	PE45609	$39.24				46
			0.02 inch Pin with .481 inch Hole Spacing	PE45601	$37.95				47
	Female, 4 Hole Flange Mount								
Cable Connectors		Clamp/ Non-Solder Contact	PE-047SR, PE-SR047FL	PE44905	$126.59	See Web for Volume Pricing			48
		Solder/ Non-Solder Contact	RG405, PE-SR405FL	PE44904	$125.61				49
Field Replaceable		Field Replaceable	0.009 inch Pin	PE45590	$45.40				50
			0.009 inch Pin with .340 inch Hole Spacing	PE45594	$46.73				51
			0.012 inch Pin	PE45591	$36.32				52
			0.012 inch Pin with .340 inch Hole Spacing	PE45595	$37.39				53
			0.015 inch Pin	PE45592	$38.14				54
			0.015 inch Pin with .340 inch Hole Spacing	PE45596	$39.26				55
			0.02 inch Pin	PE45593	$39.95				56
			0.02 inch Pin with .340 inch Hole Spacing	PE45597	$37.46				57

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

3.5mm Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	PRICE See Web for Volume Pricing			ROW
	Male								
Cable Connectors		Clamp/Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE4981	$102.12				58
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE4982	$108.11				59
	Female								
Cable Connectors		Clamp/Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE45011	$107.29		See Web for Volume Pricing		60
		Threaded	VNA Test Cable	PE45398	$688.39				61
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	PE-SR402AL, PE-SR402FL, RG402 with .235 inch D Hole	PE4985	$294.90				62

4.1/9.5 Mini DIN Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	PRICE 25-49	PRICE 50-99	PRICE 100 +	ROW
	Male								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45650	$16.24	$15.43	$14.62	$13.97	63
			SPP-250-LLPL	PE45421	$30.31	$28.79	$27.28	$26.07	64
	Male Right Angle								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45651	$21.28	$20.22	$19.15	$18.30	65
			SPP-250-LLPL	PE45422	$41.66	$39.58	$37.49	$35.83	66
			SPP-250-LLPL	TC-SPP250-4195M-RALP	$19.71	$19.71	$19.71	$19.71	67
	Female								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45652	$20.16	$19.15	$18.14	$17.34	68
			SPP-250-LLPL	PE45420	$34.08	$32.38	$30.67	$29.31	69
			TFT-402, TFT-402-LF	TC-402-4195F-LP	$13.20	$13.20	$13.20	$13.20	70
	Female, Bulkhead Mount								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45653	$22.96	$21.81	$20.66	$19.75	71

4.3-10 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	PRICE 25-49	PRICE 50-99	PRICE 100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	RG213, RG8, RG225, RG214, RG393	PE45295	$48.07	$45.67	$43.26	$41.34	72
			RG213, RG8, RG225, RG214, RG393	PE45296	$73.08	$69.43	$65.77	$62.85	73
		Crimp/ Non-Solder Contact	LMR-240	EZ-240-4310M-X	$22.17	$22.17	$22.17	$22.17	74
		Crimp/Solder	LMR-240	TC-240-4310M-X	$22.17	$22.17	$22.17	$22.17	75
			LMR-400	TC-400-4310M-X	$22.79	$22.79	$22.79	$22.79	76
			LMR-600	TC-600-4310M-X	$24.64	$24.64	$24.64	$24.64	77
		Solder/Solder	PE-1/2SFHC	PE45299	$20.03	$19.03	$18.03	$17.23	78
			PE-1/2SFHC	PE45300	$32.30	$30.69	$29.07	$27.78	79
			PE-1/4SFHC	PE45298	$19.75	$18.76	$17.78	$16.99	80

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

4.3-10 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Solder/Solder	PE-1/4SFHC	PE45297	$45.44	$43.17	$40.90	$39.08	81
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45654	$19.04	$18.09	$17.14	$16.37	82
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45658	$20.16	$19.15	$18.14	$17.34	83
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45659	$19.04	$18.09	$17.14	$16.37	84
			RG402, PE-SR402AL, PE-SR402FL, PE-SR402FLJ	PE45301	$33.65	$31.97	$30.29	$28.94	85
			SPO-375, SPF-375, SPP-375-LLPL	TC-375-4310M-LP	$18.48	$18.48	$18.48	$18.48	86
			SPP-250-LLPL	PE45418	$31.55	$29.97	$28.40	$27.13	87
			SPP-500-LLPL, SPO-500, SPF-500	TC-500-4310M-LP	$18.48	$18.48	$18.48	$18.48	88
			TFT-402, TFT-402-LF	TC-402-4310MS-LP	$20.90	$20.90	$20.90	$20.90	89
			TFT-402, TFT-402-LF	TC-402-4310M-LP	$19.80	$19.80	$19.80	$19.80	90
	Male Right Angle								
Cable Connectors		Solder/Solder	PE-1/2SFHC	PE45302	$51.74	$49.15	$46.57	$44.50	91
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45655	$21.28	$20.22	$19.15	$18.30	92
			RG402, PE-SR402AL, PE-SR402FL, PE-SR402FLJ	PE45303	$57.15	$54.29	$51.44	$49.15	93
			SPP-250-LLPL	PE45419	$41.66	$39.58	$37.49	$35.83	94
			SPP-250-LLPL, SPO-250, SPF-250	TC-250-4310M-RA-LP	$19.71	$19.71	$19.71	$19.71	95
			TFT-402, TFT-402-LF	TC-402-4310M-RA-LP	$20.90	$20.90	$20.90	$20.90	96
	Female								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45656	$20.16	$19.15	$18.14	$17.34	97
			SPP-250-LLPL	PE45417	$34.08	$32.38	$30.67	$29.31	98
			SPP-250-LLPL, SPO-250, SPF-250	TC-SPP250-4310F-LP	$18.48	$18.48	$18.48	$18.48	99
			TFT-402, TFT-402-LF	TC-402-4310F-LP	$19.80	$19.80	$19.80	$19.80	1
	Female, Bulkhead Mount								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45657	$21.28	$20.22	$19.15	$18.30	2
			TFT-402, TFT-402-LF	TC-402-4310F-BH-LP	$20.90	$20.90	$20.90	$20.90	3
	Female, 4 Hole Flange Mount								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45686	$22.40	$21.28	$20.16	$19.26	4
			RG402, PE-SR402AL, PE-SR402FL, PE-SR402FLJ	PE45304	$27.92	$26.52	$25.13	$24.01	5
Terminal		Solder	Solder Cup	PE45306	$21.97	$20.87	$19.77	$18.89	6

7/16 DIN Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	See Web for Volume Pricing			ROW
	Male								
Cable Connectors		Clamp/ Non-Solder Contact	1/2 inch Flexible, PE-1/2FAC	PE44738	$46.77	See Web for Volume Pricing			7
			1/2 inch Helical, 1/2 inch Superflexible, PE-1/2 Helical, PE-1/2SFHC	PE44732	$50.09				8
			1/4 inch Superflexible, PE-1/4SFHC	PE44728	$71.12				9
		Clamp/Solder	7/8 inch Annular	PE44993	$51.23				10
			7/8 inch Annular	PE44568	$62.05				11
			7/8 inch Helical	PE44558	$97.41				12
			PE-SR401AL, PE-SR401FL, RG401	PE44278	$49.09				13
			RG14, RG217	PE44276	$162.14				14
			RG17, RG218, RG219	PE44277	$177.87				15
			RG393, RG214, RG225, RG215, RG8	PE4567	$46.64				16
			RG58, RG55, RG141, RG142, RG223, RG400	PE45037	$122.01				17
		Crimp/ Non-Solder Contact	LMR-400, PE-C400, PE-B400, PE-B405	EZ-400-716M-X	$22.17				18
			LMR-600, PE-C600	EZ-600-716M-X	$27.10				19
			LMR-600, PE-C600	PE45001	$67.04				20

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

7/16 DIN Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	PRICE See Web for Volume Pricing			ROW
	Male								
Cable Connectors		Crimp/ Non-Solder Contact	PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44994	$48.29		See Web for Volume Pricing		21
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44538	$70.26				22
		Crimp/Solder	PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE44536	$44.03				23
			RG213, RG8	PE4570	$120.89				24
			RG214, RG9, RG225, RG393	PE4571	$60.97				25
			RG55, RG141, RG142, RG223, RG400	PE4568	$93.72				26
			RG58	PE4569	$107.02				27
		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45660	$16.24				28
			SPP-250-LLPL	PE45424	$34.73				29
			SPP-250-LLPL, SPO-250, SPF-250	TC-250-716M-LP	$14.78				30
			SPP-375-LLPL, SPO-375, SPF-375	TC-375-716M-LP	$14.78				31
			SPP-500-LLPL, SPO-500, SPF-500	TC-500-716M-LP	$12.32				32
			TFT-402, TFT-402-LF	TC-402-716M-LP	$15.95				33
	Male Right Angle								
Cable Connectors		Clamp/ Non-Solder Contact	1/2 inch Annular, 1/2 inch Flexible, PE-1/2FAC	PE44569	$54.36		See Web for Volume Pricing		34
			1/2 inch Helical	PE44979	$38.19				35
		Clamp/Solder	RG14, RG217	PE44282	$235.39				36
			RG213, RG214, RG8, RG9, RG225, RG393, RG215	PE44280	$140.80				37
		Crimp/ Non-Solder Contact	LMR-400, PE-C400, PE-B400, PE-B405	EZ-400-716M-RA-X	$24.64				38
		Crimp/Solder	LMR-195, LMR-195-FR, PE-C195, PE-P195	PE45046	$46.79				39
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44541	$91.30				40
			PE-C600, .600 inch, LMR-600, LMR-600-DB	PE45640	$88.46				41
		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45661	$21.28				42
			SPP-250-LLPL	PE45425	$49.22				43
			SPP-250-LLPL	TC-SPP250-716M-RA-LP	$19.71				44
			TFT-402, TFT-402-LF	TC-402-716M-RA-LP	$20.90				45
	Female								
Cable Connectors		Clamp/ Non-Solder Contact	1/2 inch Flexible, PE-1/2FAC	PE44740	$38.97		See Web for Volume Pricing		46
			1/2 inch Superflexible, PE-1/2SFHC	PE44734	$50.09				47
		Clamp/Solder	1/2 inch Helical	PE44560	$44.86				48
			PE-SR401AL, PE-SR401FL, RG401	PE44289	$123.34				49
			PE-SR402AL, PE-SR402FL, RG402	PE44290	$116.96				50
			RG14, RG217	PE44288	$160.92				51
			RG213, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE44283	$163.48				52
			RG58, RG55, RG141, RG142, RG223, RG400	PE44285	$147.04				53
		Crimp/ Non-Solder Contact	PE-C240, LMR-240, RG8X	PE44545	$66.19				54
		Crimp/Solder	PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE44544	$40.81				55
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF	PE44546	$79.58				56
			RG213, RG8	PE44284	$134.42				57
			RG214, RG9, RG225, RG393	PE4575	$165.12				58
			RG55, RG142, RG223, RG400	PE44286	$150.51				59
			RG58	PE44287	$109.16				60
		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45662	$16.24				61
			SPP-250-LLPL	PE45423	$34.08				62
			SPP-250-LLPL	TC-SPP250-716F-LP	$14.78				63

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

7/16 DIN Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	PRICE See Web for Volume Pricing			ROW
	Female								
Cable Connectors		Solder/Solder	SPP-375-LLPL, SPO-375, SPF-375	TC-SPP375-716F-LP	$14.78				64
			TFT-402, TFT-402-LF	TC-402-716F-LP	$15.95				65
	Female, Bulkhead Mount								
Cable Connectors		Crimp/Solder	.195 inch, RG58, RG141, RG303, LMR-195, LMR-195-FR, PE-C195, PE-P195 with 1.161 inch DD Hole	PE44548	$109.22		See Web for Volume Pricing		66
			.400 inch, LMR-400, LMR-400-DB, LMR-400-UF, PE-B405, PE-C400, PE-B400 with 1.161 inch DD Hole	PE44550	$94.66				67
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44549	$82.51				68
			PE-C600, LMR-600, LMR-600-DB, .600 inch with 1.161 inch DD Hole	PE44551	$113.17				69
			RG55, RG142, RG223, RG400 with 1.161 inch DD Hole	PE44656	$81.45				70
		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45663	$28.34				71
Terminal		Solder	Solder Cup	PE4572	$185.02				72
	Female, 4 Hole Flange Mount								
Cable Connectors		Clamp/Solder	RG14, RG217 with .975 inch Hole Spacing	PE44292	$199.28		See Web for Volume Pricing		73
			RG214, RG213, RG393, RG8, RG225, RG215, RG9 with .975 inch Hole Spacing	PE44291	$192.54				74
		Solder/Solder	TFT-402, TFT-402-LF	TC-402-716F-PM-LP	$17.05				75
Terminal		Field Replaceable	Slotted Contact	PE44717	$146.38				76
		Solder	Solder Cup with .975 inch Hole Spacing	PE4573	$102.08				77
			Stub	PE45000	$59.90				78
		Threaded Pin	Pin with .975 inch Hole Spacing	PE4574	$103.09				79
			Pin with .975 inch Hole Spacing	PE4574A	$41.23				80

BMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	PRICE See Web for Volume Pricing			ROW
	Plug								
PCB Mount		Solder	Thru Hole	PE45336	$40.26				81
			Thru Hole	PE45335	$63.48				82
	Plug, Bulkhead Mount								
Cable Connectors		Crimp/Solder	RG142, RG223, RG400, RG55	PE45318	$37.16		See Web for Volume Pricing		83
			RG178, RG196	PE45315	$84.28				84
			RG188-DS, RG316-DS	PE45317	$38.22				85
			RG316, RG188, RG174, PE-C100, LMR-100A	PE45316	$51.94				86
		Solder/ Non-Solder Contact	RG402, PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN	PE45314	$26.25				87
			RG402, PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN	PE45313	$62.41				88
			RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN	PE45310	$46.78				89
			RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN	PE45311	$27.21				90
	Plug, 2 Hole Flange Mount								
Field Replaceable		Field Replaceable	.012 inch Pin with .481 inch Hole Spacing	PE45345	$244.68				91
			.020 inch Pin with .481 inch Hole Spacing	PE45346	$233.67				92
			.036 inch Pin with .481 inch Hole Spacing	PE45348	$78.11				93

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

BMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	PRICE See Web for Volume Pricing				ROW
	Plug, 2 Hole Flange Mount									
Terminal		Solder	Stub with .481 inch Hole Spacing	PE45347	$70.95					94
			Stub with .481 inch Hole Spacing	PE45341	$42.90					95
			Stub with .481 inch Hole Spacing	PE45342	$38.71					96
			Stub with .481 inch Hole Spacing	PE45343	$12.88					97
			Stub with .481 inch Hole Spacing	PE45344	$21.82					98
	Plug, 4 Hole Flange Mount									
Terminal		Solder	Stub with .340 inch Hole Spacing	PE45339	$39.30		See Web for Volume Pricing			99
	Plug, Thread-In									
Terminal		None	Pin	PE45350	$113.33					1
			Pin	PE45351	$69.33					2
			Pin	PE45352	$129.45					3
			Pin	PE45353	$142.48					4
	Plug Right Angle									
PCB Mount		Solder	Surface Mount	PE45333	$144.82					5
			Thru Hole	PE45355	$41.86					6
	Jack									
Cable Connectors		Crimp/Solder	RG142, RG223, RG400, RG55	PE45320	$110.17		See Web for Volume Pricing			7
			RG316, RG188, RG174, PE-C100, LMR-100A	PE45319	$84.41					8
		Solder/ Non-Solder Contact	RG402, PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN	PE45328	$82.13					9
		Solder/Solder	RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ	PE45324	$74.91					10
			RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ	PE45325	$106.56					11
PCB Mount		Solder	Surface Mount	PE45338	$61.46					12
			Thru Hole	PE45337	$54.93					13
Terminal			Stub	PE45349	$197.46					14
	Jack, Bulkhead Mount									
Cable Connectors		Solder/Solder	RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ	PE45323	$48.60					15
	Jack, 2 Hole Flange Mount									
Cable Connectors		Crimp/Solder	RG316, RG188, RG174, LMR-100A, PE-C100-LSZH	PE45321	$54.89		See Web for Volume Pricing			16
		Solder/ Non-Solder Contact	RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ	PE45322	$57.50					17
		Solder/Solder	RG402, PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN	PE45326	$62.34					18
			RG402, PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN	PE45327	$39.76					19
Terminal		Solder	Stub	PE45340	$63.58					20
	Jack, 4 Hole Flange Mount									
Terminal		Solder	Stub with .340 inch Hole Spacing	PE45334	$62.69					21

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

BMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Jack, Thread-In								
Terminal		None	Pin	PE45354	$65.64	$62.36	$59.08	$56.45	22
	Jack Right Angle, 2 Hole Flange Mount								
Cable Connectors		Crimp/Solder	RG142, RG223, RG400, RG55	PE45332	$61.15	$58.09	$55.04	$52.59	23
		Solder/Solder	RG402, PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN	PE45329	$73.68	$70.00	$66.31	$63.36	24
			RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ	PE45330	$80.24	$76.23	$72.22	$69.01	25
			RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ	PE45331	$67.56	$64.18	$60.80	$58.10	26

BNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	LMR-240, PE-C240	TC-240-BMC	$19.79	$19.79	$19.79	$19.79	27
			PE-B150, RG180, RG195	PE4383	$42.80	$40.66	$38.52	$36.81	28
			PE-B400, PE-B405, PE-C400, LMR-400, .400 inch	PE4386	$31.40	$29.83	$28.26	$27.00	29
			PE-C200	PE44040	$18.17	$17.26	$16.35	$15.63	30
			PE-C300	PE44042	$16.67	$15.84	$15.00	$14.34	31
			PE-SR401AL, PE-SR401FL, RG401	PE4380	$25.55	$24.27	$23.00	$21.97	32
			PE-SR402AL, PE-SR402FL, RG402	PE4206	$23.40	$22.23	$21.06	$20.12	33
			PE-SR405AL, PE-SR405FL, RG405	PE4207	$26.41	$25.09	$23.77	$22.71	34
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE4084	$16.84	$16.00	$15.16	$14.48	35
			RG178, RG196	PE4384	$18.97	$18.02	$17.07	$16.31	36
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4023	$10.08	$9.68	$9.37	$9.17	37
			RG59*, RG62*, RG71	PE4024	$11.88	$11.29	$10.69	$10.22	38
			RG6	PE4377	$19.47	$18.50	$17.52	$16.74	39
			RG8, RG215, RG225, RG214, RG393, RG213	PE4109	$21.81	$20.72	$19.63	$18.76	40
			RG8X, PE-C240, .240 inch, B7808A, LMR-240	PE4379	$21.16	$20.10	$19.04	$18.20	41
		Crimp/Crimp	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100, LMR-100-FR, PE-C100, PE-B100	PE45045	$8.58	$8.15	$7.72	$7.38	42
			RG316-DS, RG188-DS	PE45114	$9.48	$9.01	$8.53	$8.15	43
			RG59*, RG62*, RG71	PE4018	$10.93	$10.38	$9.84	$9.40	44
		Crimp/ Non-Solder Contact	LMR-400, PE-C400, LMR-400-DB	EZ-400-BM-X	$16.63	$16.63	$16.63	$16.63	45
		Crimp/Solder	LMR-200, PE-C200	TC-200-BM-X	$14.69	$14.69	$14.69	$14.69	46
			LMR-240, PE-C240	TC-240-BM-X	$12.32	$12.32	$12.32	$12.32	47
			LMR-400, PE-C400	TC-400-BM-X	$14.78	$14.78	$14.78	$14.78	48
			PE-B150, RG180, RG195	PE4247	$15.66	$14.88	$14.09	$13.47	49
			PE-B305	PE4210	$15.04	$14.29	$13.54	$12.93	50
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44640	$17.72	$16.83	$15.95	$15.24	51
			PE-C400, LMR-400	PE44294	$34.38	$32.66	$30.94	$29.57	52
			RG178, RG196	PE4643	$27.69	$26.31	$24.92	$23.81	53
			RG213, RG215, RG8	PE4378	$28.12	$26.71	$25.31	$24.18	54
			RG214, RG9, RG225, RG393	PE4351	$25.96	$24.66	$23.36	$22.33	55
			RG55, RG141, RG142, RG223, RG400	PE4044	$8.50	$8.08	$7.65	$7.31	56
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4016	$7.79	$7.40	$7.01	$6.70	57
			RG58 Plenum, RG122, RG58-P	PE4381	$28.67	$27.24	$25.80	$24.66	58
			RG59* Plenum, RG59*-P, RG302	PE4382	$20.81	$19.77	$18.73	$17.90	59
		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE4974	$43.25	$41.09	$38.93	$37.20	60
			PE-SR401AL, PE-SR401FL, RG401	PE4908	$54.43	$51.71	$48.99	$46.81	61
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE4650	$12.65	$12.02	$11.39	$10.88	62
			PE-SR405AL, PE-SR405FL, RG405	PE4651	$28.93	$27.48	$26.04	$24.88	63

Connectors

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

BNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male, Bulkhead Mount								
Terminal		Solder	Solder Cup with .350 inch D Hole	PE4211	$18.33	$17.41	$16.50	$15.76	64
	Male, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .531 inch Hole Spacing	PE4082	$20.08	$19.08	$18.07	$17.27	65
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE4307	$54.29	$51.58	$48.86	$46.69	66
			RG178, RG196	PE4388	$26.85	$25.51	$24.17	$23.09	67
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4387	$41.75	$39.66	$37.58	$35.91	68
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4053	$21.52	$20.44	$19.37	$18.51	69
			RG59*, RG62*	PE4320	$27.59	$26.21	$24.83	$23.73	70
		Crimp/Crimp	RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4298	$27.41	$26.04	$24.67	$23.57	71
		Crimp/Solder	PE-C200, LMR-200	PE44843	$22.25	$21.14	$20.03	$19.14	72
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44641	$28.62	$27.19	$25.76	$24.61	73
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE4393	$25.90	$24.61	$23.31	$22.27	74
			RG188-DS, RG316-DS	PE4396	$32.66	$31.03	$29.39	$28.09	75
			RG55, RG141, RG142, RG223, RG400	PE4345	$12.63	$12.00	$11.37	$10.86	76
			RG59*, RG62*, RG71	PE4195	$28.72	$27.28	$25.85	$24.70	77
		Solder/Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE4092	$41.81	$39.72	$37.63	$35.96	78
			PE-SR405AL, PE-SR405FL, RG405	PE45239	$43.55	$41.37	$39.20	$37.45	79
	Female								
Cable Connectors		Clamp/Solder	PE-SR401AL, PE-SR401FL, RG401	PE44674	$33.71	$32.02	$30.34	$28.99	80
			PE-SR402AL, PE-SR402FL, RG402	PE4204	$31.44	$29.87	$28.30	$27.04	81
			PE-SR405AL, PE-SR405FL, RG405	PE4205	$32.66	$31.03	$29.39	$28.09	82
			RG174, RG316, RG188	PE4321	$16.02	$15.22	$14.42	$13.78	83
			RG178, RG196	PE4389	$21.49	$20.42	$19.34	$18.48	84
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4212	$50.69	$48.16	$45.62	$43.59	85
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4058	$13.25	$12.59	$11.93	$11.40	86
			RG59*, RG62*, RG71	PE4057	$11.51	$10.93	$10.36	$9.90	87
		Crimp/Solder	PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE4070	$10.68	$10.15	$9.61	$9.18	88
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44642	$9.11	$8.65	$8.20	$7.83	89
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4079	$13.88	$13.19	$12.49	$11.94	90
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE45395	$15.94	$14.82	$13.71	$12.75	91
			RG55, RG141, RG142, RG223, RG400	PE4397	$12.41	$11.79	$11.17	$10.67	92
			RG59*, RG62*, RG71	PE4308	$10.34	$9.82	$9.31	$8.89	93
		Solder/Solder	PE-SR401FL, PE-SR401AL, RG401	PE45150	$33.99	$32.29	$30.59	$29.23	94
PCB Mount		Solder	End Launch	PE44616	$15.43	$14.66	$13.89	$13.27	95
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	PE-SR402AL, PE-SR402FL, RG402	PE4915	$38.12	$36.21	$34.31	$32.78	96
			PE-SR405AL, PE-SR405FL, RG405	PE4916	$35.29	$33.53	$31.76	$30.35	97
			RG174, RG316, RG188 with .480 inch D Hole	PE4319	$19.75	$18.76	$17.78	$16.99	98
			RG178, RG196 with .480 inch D Hole	PE4391	$23.78	$22.59	$21.40	$20.45	99
			RG214, RG213, RG393, RG8, RG225, RG11*, RG216*, RG144*, RG215, RG9 with .480 inch D Hole	PE4632	$54.77	$52.03	$49.29	$47.10	1
			RG316-DS, RG188-DS	PE44886	$33.96	$32.26	$30.56	$29.21	2

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

BNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG58, RG142, RG223, RG400, RG141, RG303, RG55, LMR-195, PE-C195, PE-P195 with .480 inch D Hole	PE4078	$22.94	$21.79	$20.65	$19.73	3
		Crimp/Crimp	RG58, PE-C195, PE-P195, LMR-195	PE45064	$17.01	$16.16	$15.31	$14.63	4
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch with .480 inch D Hole	PE4106	$17.94	$17.04	$16.15	$15.43	5
			RG178, RG196 with .480 inch D Hole	PE44658	$24.52	$23.29	$22.07	$21.09	6
			RG188-DS, RG316-DS with .480 inch D Hole	PE4392	$21.89	$20.80	$19.70	$18.83	7
			RG316, RG174, LMR-100	PE45131	$35.69	$33.91	$32.12	$30.69	8
			RG55, RG142, RG223, RG400, RG141 with .480 inch D Hole	PE4209	$22.84	$21.70	$20.56	$19.64	9
			RG58 with .480 inch D Hole	PE4208	$15.71	$14.92	$14.14	$13.51	10
			RG59*, RG62*, RG71 with .480 inch D Hole	PE4309	$22.17	$21.06	$19.95	$19.07	11
PCB Mount		Solder	End Launch with .500 inch Diameter	PE44618	$22.81	$21.67	$20.53	$19.62	12
Terminal			Eyelet	PE44890	$30.46	$28.94	$27.41	$26.20	13
			Eyelet	PE44891	$100.93	$95.88	$90.84	$86.80	14
			Solder Cup with .350 inch D Hole	PE4015	$10.11	$9.60	$9.10	$8.69	15
			Solder Cup with .350 inch D Hole	PE4091	$10.82	$10.28	$9.74	$9.31	16
			Solder Cup with .410 inch D Hole	PE4014	$8.84	$8.40	$7.96	$7.60	17
			Solder Cup with .480 inch D Hole	PE4318	$22.32	$21.20	$20.09	$19.20	18
			Spade with .350 inch D Hole	PE4077	$27.56	$26.18	$24.80	$23.70	19
			Turret with .480 inch D Hole	PE4049	$21.16	$20.10	$19.04	$18.20	20
	Female, 4 Hole Flange Mount								
Cable Connectors		Clamp/Solder	RG316-DS, RG188-DS	PE44887	$42.81	$40.67	$38.53	$36.82	21
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, LMR-195, PE-C195, PE-P195 with .500 inch Threaded Hole Spacing	PE4056	$20.50	$19.48	$18.45	$17.63	22
		Solder/Solder	PE-047SR, PE-SR047FL, PE-SR047AL	PE44888	$44.80	$42.56	$40.32	$38.53	23
Terminal		Field Replaceable	Slotted Contact	PE44720	$58.28	$55.37	$52.45	$50.12	24
		Solder	Solder Cup with .500 inch Threaded Hole Spacing	PE4010	$11.17	$10.61	$10.05	$9.61	25
			Solder Cup with .500 inch Hole Spacing	PE4394	$15.92	$15.12	$14.33	$13.69	26
			Solder Cup with .718 inch Hole Spacing	PE4395	$27.66	$26.28	$24.89	$23.79	27
			Turret with .531 inch Hole Spacing	PE4011	$23.02	$21.87	$20.72	$19.80	28
	Female Right Angle, Bulkhead Mount								
Terminal		Solder	Solder Cup with .361 inch D Hole	PE4055	$30.55	$29.02	$27.50	$26.27	29
	Female Right Angle, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .531 inch Hole Spacing	PE4317	$36.08	$34.28	$32.47	$31.03	30

Reverse Polarity BNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	PE-SR402AL, PE-SR402FL, RG402	PE4722	$26.24	$24.93	$23.62	$22.57	31
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4719	$40.63	$38.60	$36.57	$34.94	32
			RG178, RG196	PE4721	$29.76	$28.27	$26.78	$25.59	33
			RG213, RG214, RG8, RG9, RG225, RG393, RG215	PE4711	$40.63	$38.60	$36.57	$34.94	34
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4714	$40.26	$38.25	$36.23	$34.62	35

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

Reverse Polarity BNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	RG59*, RG62*	PE4717	$16.79	$15.95	$15.11	$14.44	36
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4720	$27.37	$26.00	$24.63	$23.54	37
			RG213, RG8	PE4712	$32.61	$30.98	$29.35	$28.04	38
			RG214, RG9, RG225, RG393	PE4713	$34.83	$33.09	$31.35	$29.95	39
			RG55, RG141, RG142, RG223, RG400	PE4715	$16.68	$15.85	$15.01	$14.34	40
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4716	$19.96	$18.96	$17.96	$17.17	41
			RG59*, RG62*	PE4718	$18.92	$17.97	$17.03	$16.27	42
	Male, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .531 inch Hole Spacing	PE4762	$27.55	$26.17	$24.80	$23.69	43
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188	PE4732	$28.11	$26.70	$25.30	$24.17	44
			RG213, RG214, RG8, RG9, RG225, RG393, RG215	PE4727	$50.34	$47.82	$45.31	$43.29	45
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4728	$27.96	$26.56	$25.16	$24.05	46
		Crimp/Solder	RG174, RG316, RG188	PE4733	$27.30	$25.94	$24.57	$23.48	47
			RG55, RG141, RG142, RG223, RG400	PE4729	$27.80	$26.41	$25.02	$23.91	48
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4730	$33.23	$31.57	$29.91	$28.58	49
	Female								
Cable Connectors		Clamp/Solder	PE-SR402AL, PE-SR402FL, RG402	PE4744	$26.73	$25.39	$24.06	$22.99	50
			PE-SR405AL, PE-SR405FL, RG405	PE4745	$27.02	$25.67	$24.32	$23.24	51
			RG174, RG316, RG188	PE4741	$33.74	$32.05	$30.37	$29.02	52
			RG178, RG196	PE4743	$33.74	$32.05	$30.37	$29.02	53
			RG213, RG214, RG8, RG9, RG225, RG393	PE4735	$41.90	$39.81	$37.71	$36.03	54
			RG55, RG58, RG141, RG142, RG223, RG400	PE4736	$40.63	$38.60	$36.57	$34.94	55
		Crimp/Solder	RG174, RG316, RG188	PE4742	$28.72	$27.28	$25.85	$24.70	56
			RG188-DS, RG316-DS	PE45182	$25.35	$24.08	$22.82	$21.80	57
			RG55, RG141, RG142, RG223, RG400	PE4737	$25.45	$24.18	$22.91	$21.89	58
			RG58	PE4738	$29.27	$27.81	$26.34	$25.17	59
			RG59*, RG62*	PE4739	$27.83	$26.44	$25.05	$23.93	60
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	PE-SR405AL, PE-SR405FL, RG405 with .480 inch D Hole	PE4755	$28.11	$26.70	$25.30	$24.17	61
			RG174, RG316, RG188 with .480 inch D Hole	PE4751	$25.75	$24.46	$23.18	$22.15	62
			RG55, RG58, RG141, RG142, RG223, RG400 with .480 inch D Hole	PE4746	$42.58	$40.45	$38.32	$36.62	63
			RG59*, RG62* with .480 inch D Hole	PE4749	$38.08	$36.18	$34.27	$32.75	64
		Crimp/Solder	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100A-FR, PE-C100, PE-B100 with .480 inch D Hole	PE4752	$30.76	$29.22	$27.68	$26.45	65
			RG55, RG142, RG223, RG400 with .480 inch D Hole	PE4747	$28.11	$26.70	$25.30	$24.17	66
			RG58, RG141 with .480 inch D Hole	PE4748	$29.60	$28.12	$26.64	$25.46	67
Terminal		Solder	Solder Cup with .350 inch D Hole	PE4758	$16.87	$16.03	$15.18	$14.51	68
			Solder Cup with .410 inch D Hole	PE4757	$18.38	$17.46	$16.54	$15.81	69
			Solder Cup with .480 inch D Hole	PE4764	$26.69	$25.36	$24.02	$22.95	70
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .500 inch Threaded Hole Spacing	PE4756	$28.14	$26.73	$25.33	$24.20	71
			Solder Cup with .500 inch Hole Spacing	PE4763	$28.15	$26.74	$25.34	$24.21	72
	Female Right Angle, Bulkhead Mount								
Terminal		Solder	Solder Cup with .361 inch D Hole	PE4759	$49.36	$46.89	$44.42	$42.45	73

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

C Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	RG14, RG217	PE4951	$67.73	$64.34	$60.96	$58.25	74
			RG174, RG316, RG188	PE4953	$39.63	$37.65	$35.67	$34.08	75
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4950	$53.96	$51.26	$48.56	$46.41	76
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4243	$69.37	$65.90	$62.43	$59.66	77
			RG218	PE4954	$98.88	$93.94	$88.99	$85.04	78
			RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE4242	$54.44	$51.72	$49.00	$46.82	79
			RG59*, RG62*, RG71	PE4952	$54.60	$52.42	$50.78	$49.69	80
		Crimp/Solder	RG213, RG8	PE4518	$39.63	$37.65	$35.67	$34.08	81
			RG214, RG9, RG225, RG393	PE4375	$30.20	$28.69	$27.18	$25.97	82
			RG55, RG141, RG142, RG223, RG400	PE4445	$31.53	$29.95	$28.38	$27.12	83
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4517	$41.97	$39.87	$37.77	$36.09	84
	Male, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .718 inch Hole Spacing	PE44096	$76.85	$73.01	$69.17	$66.09	85
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4244	$74.03	$70.33	$66.63	$63.67	86
			RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE4957	$99.28	$94.32	$89.35	$85.38	87
		Crimp/Solder	PE-P195, PE-C195, RG58, RG141, RG303, .195 inch, LMR-195	PE4959	$96.57	$91.74	$86.91	$83.05	88
			RG213, RG8	PE4955	$79.50	$75.53	$71.55	$68.37	89
			RG214, RG9, RG225, RG393	PE4949	$92.66	$88.03	$83.39	$79.69	90
			RG55, RG141, RG142, RG223, RG400	PE4958	$75.96	$72.16	$68.36	$65.33	91
	Female								
Cable Connectors		Clamp/Solder	RG14, RG217	PE4963	$76.23	$72.42	$68.61	$65.56	92
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4960	$61.41	$58.34	$55.27	$52.81	93
			RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE4961	$82.35	$78.23	$74.12	$70.82	94
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG214, RG213, RG393, RG8, RG225, RG11*, RG216*, RG144*, RG215, RG9 with .720 inch D Hole	PE4964	$73.81	$70.12	$66.43	$63.48	95
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, LMR-400, PE-C195, PE-P195 with .596 inch D Hole	PE44099	$77.76	$73.87	$69.98	$66.87	96
			RG58, RG55, RG141, RG142, RG223, RG400 with .720 inch D Hole	PE4965	$87.02	$82.67	$78.32	$74.84	97
			RG59*, RG62* with .596 inch D Hole	PE44098	$35.03	$33.28	$31.53	$30.13	98
Terminal		Solder	Solder Cup with .720 inch D Hole	PE4240	$59.33	$56.96	$55.18	$53.99	99
			Solder Cup with .720 inch D Hole	PE4971	$83.12	$78.96	$74.81	$71.48	1
			Solder Cup with .720 inch D Hole	PE4972	$83.12	$78.96	$74.81	$71.48	2
			Turret with .350 inch D Hole	PE4973	$87.31	$82.94	$78.58	$75.09	3
	Female, 4 Hole Flange Mount								
Cable Connectors		Clamp/Solder	RG213, RG214, RG393, RG11*	PE4CO1013	$80.32	$76.30	$72.29	$69.08	4
			RG214, RG213, RG393, RG8, RG225, RG11*, RG216*, RG144*, RG215, RG9 with .718 inch Hole Spacing	PE4967	$88.13	$83.72	$79.32	$75.79	5
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, LMR-400, PE-C195, PE-P195 with .718 inch Hole Spacing	PE4969	$64.24	$61.03	$57.82	$55.25	6
		Crimp/Solder	RG214, RG9, RG225, RG393 with .718 inch Hole Spacing	PE4374	$74.05	$70.35	$66.65	$63.68	7
Terminal		Solder	Solder Cup with .718 inch Hole Spacing	PE4241	$27.58	$26.20	$24.82	$23.72	8

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

D-Sub Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Receptacle								
Cable Connectors		Crimp/Solder	PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE4800	$17.68	$16.80	$15.91	$15.20	9
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE4801	$19.45	$18.48	$17.51	$16.73	10
		Solder/Solder	RG180, RG195	PE4807	$9.62	$9.14	$8.66	$8.27	11
			RG55, RG142, RG223, RG400	PE4838	$14.83	$14.09	$13.35	$12.75	12
			RG58, RG141, RG303	PE4804	$15.14	$14.38	$13.63	$13.02	13
	Receptacle Right Angle								
Cable Connectors		Crimp/Solder	RG58, RG141, RG303	PE4816	$28.53	$27.39	$26.53	$25.96	14
	Plug								
Cable Connectors		Crimp/Solder	PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE4808	$17.70	$16.82	$15.93	$15.22	15
		Solder/Solder	RG180, RG195, PE-B150	PE4815	$20.90	$19.86	$18.81	$17.97	16
			RG58, RG141, RG303	PE4812	$14.72	$13.98	$13.25	$12.66	17
	Plug Right Angle								
Cable Connectors		Solder/Solder	PE-SR405AL, PE-SR405FL, RG405	PE44038	$23.87	$22.92	$22.20	$21.72	18

D-Subminiature Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug Right Angle								
Cable Connectors		Solder/Solder	RG55, RG142, RG223, RG400	PE44036	$15.61	$14.83	$14.05	$13.42	19

FAKRA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Black Color	PE45404A	$6.32	$6.00	$5.69	$5.44	20
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with White Color	PE45404B	$6.32	$5.88	$5.44	$5.06	21
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Blue Color	PE45404C	$6.32	$6.00	$5.69	$5.44	22
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Bordeaux Color	PE45404D	$6.32	$6.00	$5.69	$5.44	23
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Violet Color	PE45404H	$6.32	$6.00	$5.69	$5.44	24
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Beige Color	PE45404I	$6.32	$6.00	$5.69	$5.44	25
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Curry Color	PE45404K	$6.32	$6.00	$5.69	$5.44	26
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Water Blue Color	PE45404Z	$6.32	$6.00	$5.69	$5.44	27
PCB Mount		Solder	Thru Hole with Black Color	PE44649A	$7.10	$6.75	$6.39	$6.11	28
			Thru Hole with White Color	PE44649B	$3.48	$3.31	$3.13	$2.99	29
			Thru Hole with Blue Color	PE44649C	$7.10	$6.75	$6.39	$6.11	30
			Thru Hole with Bordeaux Color	PE44649D	$3.98	$3.78	$3.58	$3.42	31
			Thru Hole with Violet Color	PE44649H	$3.48	$3.31	$3.13	$2.99	32
			Thru Hole with Beige Color	PE44649I	$5.60	$5.32	$5.04	$4.82	33
			Thru Hole with Curry Color	PE44649K	$3.48	$3.31	$3.13	$2.99	34
			Thru Hole with Water Blue Color	PE44649Z	$7.32	$6.95	$6.59	$6.30	35

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

FAKRA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug Right Angle								
PCB Mount		Solder	Thru Hole with Black Color	PE44651A	$9.93	$9.43	$8.94	$8.54	36
			Thru Hole with White Color	PE44651B	$5.98	$5.68	$5.38	$5.14	37
			Thru Hole with Blue Color	PE44651C	$9.93	$9.43	$8.94	$8.54	38
			Thru Hole with Bordeaux Color	PE44651D	$8.85	$8.41	$7.97	$7.61	39
			Thru Hole with Violet Color	PE44651H	$7.39	$7.02	$6.65	$6.36	40
			Thru Hole with Beige Color	PE44651I	$7.39	$7.02	$6.65	$6.36	41
			Thru Hole with Curry Color	PE44651K	$7.91	$7.51	$7.12	$6.80	42
			Thru Hole with Water Blue Color	PE44651Z	$9.14	$8.68	$8.23	$7.86	43
	Jack								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Black Color	PE44646A	$8.17	$7.76	$7.35	$7.03	44
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with White Color	PE44646B	$8.17	$7.76	$7.35	$7.03	45
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Blue Color	PE44646C	$8.17	$7.76	$7.35	$7.03	46
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Bordeaux Color	PE44646D	$7.10	$6.75	$6.39	$6.11	47
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Violet Color	PE44646H	$8.17	$7.76	$7.35	$7.03	48
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Beige Color	PE44646I	$7.28	$6.92	$6.55	$6.26	49
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Curry Color	PE44646K	$8.17	$7.76	$7.35	$7.03	50
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Water Blue Color	PE44646Z	$7.52	$7.14	$6.77	$6.47	51
			RG188-DS, RG316-DS with Black Color	PE45176	$6.22	$5.91	$5.60	$5.35	52
			RG316-DS, RG188-DS with Water Blue Color	PE45176Z	$5.89	$5.48	$5.07	$4.71	53
	Jack Right Angle								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Black Color	PE44648A	$9.93	$9.43	$8.94	$8.54	54
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with White Color	PE44648B	$9.93	$9.43	$8.94	$8.54	55
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Blue Color	PE44648C	$9.93	$9.43	$8.94	$8.54	56
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Bordeaux Color	PE44648D	$7.91	$7.51	$7.12	$6.80	57
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Violet Color	PE44648H	$8.85	$8.41	$7.97	$7.61	58
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Beige Color	PE44648I	$5.73	$5.44	$5.16	$4.93	59
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Curry Color	PE44648K	$8.85	$8.41	$7.97	$7.61	60
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with Water Blue Color	PE44648Z	$9.58	$9.10	$8.62	$8.24	61
PCB Mount		Solder	Thru Hole with Black Color	PE44650A	$5.65	$5.37	$5.09	$4.86	62
			Thru Hole with White Color	PE44650B	$8.12	$7.71	$7.31	$6.98	63
			Thru Hole with Blue Color	PE44650C	$7.07	$6.72	$6.36	$6.08	64
			Thru Hole with Bordeaux Color	PE44650D	$5.92	$5.62	$5.33	$5.09	65
			Thru Hole with Violet Color	PE44650H	$4.96	$4.71	$4.46	$4.27	66
			Thru Hole with Beige Color	PE44650I	$5.98	$5.68	$5.38	$5.14	67
			Thru Hole with Water Blue Color	PE44650Z	$10.37	$9.85	$9.33	$8.92	68

FME Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188	PE44297	$13.42	$12.75	$12.08	$11.54	69
			RG55, RG142, RG223, RG400	PE44296	$12.16	$11.55	$10.94	$10.46	70
			RG58	PE44295	$14.80	$14.06	$13.32	$12.73	71
	Plug, Bulkhead Mount								
Terminal		Solder	Solder Cup with .350 inch D Hole	PE44149	$9.54	$9.06	$8.59	$8.20	72

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

FME Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Jack								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188	PE44148	$13.86	$13.17	$12.47	$11.92	73
			RG55, RG142, RG223, RG400	PE44147	$9.91	$9.41	$8.92	$8.52	74
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE44146	$11.32	$10.75	$10.19	$9.74	75

GR874 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Sexless								
Cable Connectors		Accessories		PE4348	$52.60	$49.97	$47.34	$45.24	76
		Crimp/Solder	RG214, RG9, RG225, RG393	PE4352	$95.75	$90.96	$86.18	$82.35	77
			RG55, RG58, RG141, RG142, RG223, RG400	PE4233	$30.76	$29.22	$27.68	$26.45	78

HN Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	See Web for Volume Pricing			ROW
	Male								
Cable Connectors		Clamp/Solder	RG14, RG217	PE4475	$51.61	See Web for Volume Pricing			79
			RG17, RG218, RG219	PE4476	$137.88				80
			RG213, RG214, RG8, RG9, RG225, RG393	PE4182	$28.84				81
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4198	$39.11				82
			RG59*, RG62*, RG71	PE4479	$62.01				83
		Crimp/Solder	RG213, RG215, RG8	PE4473	$45.86				84
			RG214, RG9, RG225, RG393	PE4474	$47.50				85
			RG55, RG142, RG223, RG400, RG141	PE4477	$43.17				86
			RG58, RG141	PE4478	$38.12				87
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG14, RG217	PE45307	$83.12				88
			RG213, RG8, RG393, RG225, RG214, RG393, RG9	PE4230	$69.50				89
			RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE4480	$83.73				90
	Female								
Cable Connectors		Clamp/Solder	RG213, RG8, RG225, RG214, RG393	PE4229	$63.89		See Web for Volume Pricing		91
			RG401, PE-SR401AL, PE-SR401FL	PE4229-401	$63.89				92
	Female, Bulkhead Mount								
Terminal		Solder	Turret with .765 inch DD Hole	PE4481	$69.46				93
	Female, 4 Hole Flange Mount								
Terminal		Field Replaceable	Slotted Contact	PE44718	$65.42				94
		Solder	Solder Cup with .906 inch Hole Spacing	PE4183	$34.62				95

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

LC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-9	10-24	25-49	50+	ROW
	Male								
Cable Connectors		Clamp/Solder	RG14, RG217	PE4563	$220.92	$209.87	$198.83	$189.99	96
			RG213, RG214, RG8, RG9, RG225, RG393, RG215	PE4564	$173.72	$165.03	$156.35	$149.40	97
			RG218, RG219, RG17	PE4323	$234.06	$222.36	$210.65	$201.29	98
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG14, RG217	PE44448	$351.96				99
			RG213, RG214, RG8, RG9, RG225, RG393, RG215	PE44447	$269.63				1
	Female								
Cable Connectors		Clamp/Solder	RG17, RG218, RG219	PE44451	$291.25		See Web for Volume Pricing		2
			RG213, RG214, RG8, RG9, RG225, RG393, RG215	PE44450	$227.68				3
	Female, 4 Hole Flange Mount								
Terminal		Solder	Pin	PE45519	$192.42				4
			Pin with 1.44 inch Hole Spacing	PE4192	$113.60				5

MC-Card Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188	PE44309	$12.35	$11.73	$11.12	$10.62	6
			RG178, RG196	PE44310	$12.35	$11.73	$11.12	$10.62	7
			RG188-DS, RG316-DS	PE45169	$12.20	$11.59	$10.98	$10.49	8
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE44308	$14.99	$14.24	$13.49	$12.89	9
			RG178, RG196	PE44311	$16.55	$15.72	$14.90	$14.23	10
			RG188-DS, RG316-DS	PE45168	$13.01	$12.36	$11.71	$11.19	11

MCX Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG178, RG196	PE4552	$20.94	$19.89	$18.85	$18.01	12
			RG188-DS, RG316-DS	PE4878	$15.05	$14.30	$13.55	$12.94	13
			RG316, RG174, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4551	$13.38	$12.71	$12.04	$11.51	14
			RG55, RG141, RG142, RG223, RG400	PE4881	$32.80	$31.49	$30.50	$29.85	15
			RG58	PE4880	$26.57	$25.51	$24.71	$24.18	16
		Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE4876	$26.18	$24.87	$23.56	$22.51	17
PCB Mount			Surface Mount	PE44613	$18.74	$17.80	$16.87	$16.12	18
			Thru Hole with .200 inch x .052 inch Hole Spacing	PE4559	$24.00	$22.80	$21.60	$20.64	19
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4553	$18.24	$17.33	$16.42	$15.69	20
			RG178, RG196	PE4554	$20.12	$19.11	$18.11	$17.30	21
			RG188-DS, RG316-DS	PE4879	$18.17	$17.26	$16.35	$15.63	22

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

MCX Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG55, RG142, RG223, RG400	PE4883	$18.23	$17.32	$16.41	$15.68	23
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4882	$22.61	$21.48	$20.35	$19.44	24
		Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE4877	$29.77	$28.28	$26.79	$25.60	25
		Solder/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44698	$9.89	$9.40	$8.90	$8.51	26
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE44830	$19.72	$18.93	$18.34	$17.95	27
	Jack								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE4562	$25.62	$24.34	$23.06	$22.03	28
			RG178, RG196	PE4884	$32.52	$30.89	$29.27	$27.97	29
			RG188-DS, RG316-DS	PE4885	$21.31	$20.24	$19.18	$18.33	30
PCB Mount		Solder	.042 inch End Launch	PE4893	$26.30	$24.99	$23.67	$22.62	31
			.062 inch End Launch	PE4892	$15.38	$14.61	$13.84	$13.23	32
			End Launch	PE44661	$23.38	$22.21	$21.04	$20.11	33
			Surface Mount	PE44660	$35.18	$33.42	$31.66	$30.25	34
			Surface Mount	PE4889	$18.04	$17.14	$16.24	$15.51	35
			Thru Hole with .200 inch x .052 inch Hole Spacing	PE4555	$15.28	$14.52	$13.75	$13.14	36
			Thru Hole with .200 inch x .067 inch Hole Spacing	PE44303	$19.37	$18.40	$17.43	$16.66	37
	Jack, Bulkhead Mount								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch with .177 inch D Hole	PE4887	$24.73	$23.49	$22.26	$21.27	38
			RG178, RG196 with .177 inch D Hole	PE4886	$27.10	$25.75	$24.39	$23.31	39
			RG188-DS, RG316-DS with .177 inch D Hole	PE4888	$19.12	$18.16	$17.21	$16.44	40
Terminal		Solder	Turret with .177 inch D Hole	PE4561	$21.30	$20.24	$19.17	$18.32	41
	Jack, 2 Hole Flange Mount								
Terminal		Solder	Pin with .328 inch Hole Spacing	PE4894	$28.53	$27.10	$25.68	$24.54	42
			Solder Cup with .328 inch Hole Spacing	PE4891	$30.26	$28.75	$27.23	$26.02	43
	Jack Right Angle								
PCB Mount		Solder	Surface Mount	PE4890	$25.01	$23.76	$22.51	$21.51	44
			Thru Hole with .200 inch x .052 inch Hole Spacing	PE4556	$18.66	$17.73	$16.79	$16.05	45
			Thru Hole with .200 inch x .052 inch Hole Spacing	PE45274	$17.11	$16.25	$15.40	$14.71	46
	Jack Right Angle, Bulkhead Mount								
Terminal		Solder	Turret with .177 inch D Hole	PE4560	$50.28	$47.77	$45.25	$43.24	47

Reverse Polarity MCX Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE44369	$27.83	$26.44	$25.05	$23.93	48
			RG178, RG196	PE44370	$27.06	$25.71	$24.35	$23.27	49
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG178, RG196	PE45051	$8.67	$8.32	$8.06	$7.89	50
			RG316, RG188, RG174	PE45050	$9.63	$9.15	$8.67	$8.28	51

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

Reverse Polarity MCX Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Jack, Bulkhead Mount								
Cable Connectors		Crimp/Solder	RG178, RG196 with .177 inch D Hole	PE44374	$33.12	$31.46	$29.81	$28.48	52
PCB Mount		Solder	End Launch with .177 inch D Hole	PE44377	$31.03	$29.48	$27.93	$26.69	53
	Jack Right Angle, Bulkhead Mount								
PCB Mount		Solder	Thru Hole with .177 inch D Hole	PE44376	$34.83	$33.09	$31.35	$29.95	54

MHV Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	See Web for Volume Pricing			ROW
	Male								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188	PE4494	$19.39	See Web for Volume Pricing			55
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4299	$35.21				56
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4076	$21.24				57
			RG59*, RG62*, RG71	PE4098	$19.40				58
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4933	$50.11				59
			RG213, RG8	PE4493	$35.60				60
			RG214, RG9, RG225, RG393	PE4350	$40.14				61
			RG55, RG141, RG142, RG223, RG400	PE4657	$22.48				62
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4093	$29.03				63
			RG59*, RG62*, RG71	PE4075	$20.95				64
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188	PE4710	$38.12				65
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393	PE4709	$67.36				66
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4226	$38.81				67
			RG59*, RG62*, RG71	PE4227	$36.17				68
	Female								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188	PE44104	$31.44	See Web for Volume Pricing			69
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4225	$28.69				70
			RG59*, RG62*, RG71	PE4181	$26.77				71
		Crimp/Solder	PE-P195, PE-C195, RG58, RG141, RG303, .195 inch, LMR-195	PE44102	$32.32				72
			RG55, RG141, RG142, RG223, RG400	PE44100	$30.37				73
			RG59*, RG62*	PE44103	$39.35				74
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188	PE44111	$53.52				75
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393	PE44105	$70.80				76
			RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE44106	$55.40				77
			RG59*, RG62*, RG71	PE44109	$51.86				78
		Crimp/Solder	RG55, RG141, RG142, RG223, RG400	PE44107	$33.00				79
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE44108	$44.62				80
			RG59*, RG62*, RG71	PE44110	$55.97				81
Terminal		Solder	Solder Cup	PE44896	$124.93				82
			Solder Cup with .480 inch D Hole	PE4495	$52.98				83
			Solder Cup with .380 inch DD Hole	PE4193	$27.94				84
			Solder Cup with .380 inch DD Hole	PE4311	$53.03				85
			Turret with .537 inch D Hole	PE4312	$43.88				86

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

MHV Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, 4 Hole Flange Mount								
Cable Connectors		Clamp/Solder	RG214, RG213, RG393, RG8, RG225, RG11*, RG216*, RG144*, RG215, RG9 with .718 inch Hole Spacing	PE44112	$59.31	$56.34	$53.38	$51.01	87
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, LMR-400, PE-C195, PE-P195 with .500 inch Threaded Hole Spacing	PE4313	$52.21	$49.60	$46.99	$44.90	88
			RG59*, RG62*, RG71 with .500 inch Threaded Hole Spacing	PE4314	$55.88	$53.09	$50.29	$48.06	89
Terminal		Solder	Solder Cup	PE45035	$62.56	$59.43	$56.30	$53.80	90
			Solder Cup with .500 inch Threaded Hole Spacing	PE4228	$35.97	$34.17	$32.37	$30.93	91

Mini SMP Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
PCB Mount		Solder	Edge Launch	PE44969	$32.79	$31.15	$29.51	$28.20	92
			End Launch	PE44490	$30.07	$28.57	$27.06	$25.86	93
			Surface Mount	PE44489	$35.58	$33.80	$32.02	$30.60	94
			Thru Hole	PE44970	$61.54	$58.46	$55.39	$52.92	95
	Male, Solder								
Terminal		Solder	Pin	PE44973	$42.81	$40.67	$38.53	$36.82	96
	Male Right Angle								
PCB Mount		Solder	Surface Mount	PE44968	$74.84	$71.10	$67.36	$64.36	97
	Female								
Cable Connectors		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44491	$43.05	$40.90	$38.75	$37.02	98
			PE-047SR, PE-SR047FL	PE44971	$49.88	$47.39	$44.89	$42.90	99
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44974	$39.68	$37.70	$35.71	$34.12	1
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44492	$42.47	$40.35	$38.22	$36.52	2
	Female Right Angle								
Cable Connectors		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44493	$55.40	$52.63	$49.86	$47.64	3
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44494	$49.84	$47.35	$44.86	$42.86	4
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44972	$64.15	$60.94	$57.74	$55.17	5

Mini UHF Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188	PE44090	$13.98	$13.28	$12.58	$12.02	6
			RG55, RG141, RG142, RG223, RG400	PE44088	$12.64	$12.01	$11.38	$10.87	7
			RG55, RG141, RG142, RG223, RG400	PE4521	$7.85	$7.46	$7.07	$6.75	8
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4342	$7.85	$7.46	$7.07	$6.75	9
	Female								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188	PE44085	$5.63	$5.35	$5.07	$4.84	10
			RG55, RG141, RG142, RG223, RG400	PE44083	$12.16	$11.55	$10.94	$10.46	11
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE44084	$15.94	$15.14	$14.35	$13.71	12
	Female, Bulkhead Mount								
Cable Connectors		Crimp/Solder	.195 inch, RG58, RG141, RG303, LMR-195, LMR-195-FR, PE-C195, PE-P195 with .410 inch D Hole	PE44087	$17.96	$17.06	$16.16	$15.45	13
			RG55, RG141, RG142, RG223, RG400 with .410 inch D Hole	PE44086	$14.83	$14.09	$13.35	$12.75	14

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

Mini UHF Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
PCB Mount		Solder	Thru Hole with .380 inch Diameter	PE44092	$13.04	$12.39	$11.74	$11.21	15
Terminal			Solder Cup with .350 inch D Hole	PE44089	$9.74	$9.25	$8.77	$8.38	16
			Solder Cup with .350 inch D Hole	PE4644	$7.76	$7.37	$6.98	$6.67	17
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .437 inch Hole Spacing	PE44091	$13.11	$12.45	$11.80	$11.27	18

MMBX Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	See Web for Volume Pricing			ROW
	Plug								
Cable Connectors		Crimp/Solder	RG178, RG196	PE45250	$13.69				19
			RG316, RG174	PE45251	$15.47				20
			RG316-DS, RG188-DS	PE45252	$12.22				21
		Solder/ Non-Solder Contact	RG405, PE-SR405FL, PE-SR405FLJ	PE45253	$15.82				22
PCB Mount		Solder/Solder	Surface Mount	PE45259TR1	$20.28				23
			Surface Mount	PE45259TR750	$9,962.61				24
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG178, RG196	PE45254	$18.12		See Web for Volume Pricing		25
			RG316, RG174	PE45255	$18.60				26
			RG316-DS, RG188-DS	PE45256	$18.12				27
		Solder/Solder	RG405, PE-SR405FL, PE-SR405FLJ	PE45257	$18.12				28
	Jack								
PCB Mount		Solder	Edge Launch	PE45261	$18.51				29
			Surface Mount	PE45262TR1	$12.64				30
			Surface Mount	PE45262TR750	$6,150.69				31
			Through Hole	PE45265TR500	$5,154.70				32
			Through Hole	PE45265TR1	$15.29				33
	Jack, Thread-In								
Terminal		Solder	Pin	PE45267	$14.21				34

MMCX Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4896	$18.54	$17.61	$16.69	$15.94	35
			RG178, RG196	PE4897	$18.09	$17.19	$16.28	$15.56	36
			RG178, RG196	PE44645	$19.55	$18.57	$17.60	$16.81	37
			RG188-DS, RG316-DS	PE44874	$20.57	$19.54	$18.51	$17.69	38
		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44456	$23.31	$22.14	$20.98	$20.05	39
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44453	$21.76	$20.67	$19.58	$18.71	40

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

MMCX Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
PCB Mount		Solder	End Launch	PE44663	$25.74	$24.45	$23.17	$22.14	41
			Thru Hole with .100 inch x .031 inch Hole Spacing	PE4905	$29.04	$27.59	$26.14	$24.97	42
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4898	$12.64	$12.01	$11.38	$10.87	43
			RG178, RG196	PE4899	$20.97	$19.92	$18.87	$18.03	44
			RG316-DS, RG188-DS	PE44784	$23.40	$22.23	$21.06	$20.12	45
		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44457	$27.79	$26.40	$25.01	$23.90	46
		Solder/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44699	$9.80	$9.31	$8.82	$8.43	47
	Jack								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE4901	$18.62	$17.69	$16.76	$16.01	48
			RG178, RG196	PE4902	$18.62	$17.69	$16.76	$16.01	49
			RG316-DS, RG188-DS	PE44852	$20.66	$19.63	$18.59	$17.77	50
		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44459	$34.20	$32.49	$30.78	$29.41	51
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44458	$32.37	$30.75	$29.13	$27.84	52
PCB Mount			Surface Mount	PE44662	$23.83	$22.64	$21.45	$20.49	53
			Thru Hole with .100 inch x .031 inch Hole Spacing	PE4904	$16.05	$15.25	$14.45	$13.80	54
	Jack Right Angle								
PCB Mount		Solder	Thru Hole with .100 inch x .031 inch Hole Spacing	PE4903	$25.48	$24.21	$22.93	$21.91	55

N Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp	7/8 inch Annular, 7/8 inch Helical, 7/8 inch Superflexible, 7/8 inch Flexible	PE44976	$63.60	$60.42	$57.24	$54.70	56
		Clamp/ Non-Solder Contact	1/2 inch Helical, 1/2 inch Superflexible, PE-1/2 Helical, PE-1/2SFHC	PE44729	$50.97	$48.42	$45.87	$43.83	57
			1/4 inch Superflexible, PE-1/4SFHC	PE44726	$64.48	$61.26	$58.03	$55.45	58
			LMR-400, PE-C400, PE-B400, PE-B405	EZ-400-NMC-2-D	$24.64	$24.64	$24.64	$24.64	59
			LMR-600, PE-C600	EZ-600-NMC-2-D	$24.64	$24.64	$24.64	$24.64	60
			PE-1/2FAC, 1/2 inch Flexible, 1/2 inch Annular	PE44735	$45.31	$43.04	$40.78	$38.97	61
		Clamp/Solder	LMR-240, PE-C240	TC-240-NMC	$18.36	$18.36	$18.36	$18.36	62
			PE-C300	PE44045	$24.56	$23.33	$22.10	$21.12	63
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE4133	$26.39	$25.33	$24.54	$24.01	64
			PE-C500, LMR-500	PE44046	$40.39	$38.37	$36.35	$34.74	65
			PE-C600, .600 inch, LMR-600	PE44349	$80.00	$76.00	$72.00	$68.80	66
			PE-P142LL	PE44825	$50.07	$47.57	$45.06	$43.06	67
			PE-P160LL	PE45446	$88.53	$84.10	$79.68	$76.14	68
			PE-P300LL	PE44809	$79.51	$75.53	$71.56	$68.38	69
			PE-SR401AL, PE-SR401FL, RG401	PE4434	$23.40	$22.23	$21.06	$20.12	70
			PE-SR402AL, PE-SR402FL, RG402	PE4006	$23.40	$22.23	$21.06	$20.12	71
			PE-SR405AL, PE-SR405FL, RG405	PE4129	$22.99	$21.84	$20.69	$19.77	72

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

N Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	PRICE See Web for Volume Pricing			ROW
	Male								
Cable Connectors		Clamp/Solder	RG14, RG217	PE4221	$35.35	See Web for Volume Pricing			73
			RG17, RG218, RG219	PE4433	$107.29				74
			RG174, RG316, RG188	PE4224	$19.39				75
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4062	$18.61				76
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4081	$15.12				77
			RG59*, RG62*, RG71	PE4331	$21.69				78
		Clamp/Solder (Captive Contact)	RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4132	$19.27				79
		Crimp/Crimp	PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE44520	$12.37				80
			RG55, RG141, RG142, RG223, RG400	PE4042	$23.07				81
		Crimp/ Non-Solder Contact	LMR-200, PE-C200	EZ-200-NMH-X	$16.00				82
			LMR-240, PE-C240, RG8X	EZ-240-NMH-X	$12.75				83
			LMR-400, PE-C400	EZ-400-NMH-PL-X	$15.40				84
			LMR-400, PE-C400, PE-B400, PE-B405	EZ-400-NMH-X	$14.78				85
			LMR-600, PE-C600	EZ-600-NMH-X	$21.56				86
		Crimp/Solder	LMR-195, PE-C195	TC-195-NMH-X	$13.25				87
			LMR-200, PE-C200	TC-200-NMH-X	$17.14				88
			LMR-240, PE-C240	TC-240-NMH-X	$15.09				89
			LMR-400, PE-C400, PE-B405	TC-400-NMH-X	$14.78				90
			LMR-600, PE-C600	TC-600-NMH-X	$20.33				91
			PE-B400, PE-B405, PE-C400, LMR-400, .400 inch	PE4550	$17.23				92
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44521	$18.04				93
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44522	$21.37				94
			PE-C600, LMR-600, LMR-600-DB, .600 inch	PE44454	$36.66				95
			PE-C600, LMR-600, LMR-600-DB, .600 inch	PE44523	$70.85				96
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4429	$21.87				97
			RG178, RG196	PE4647	$30.48				98
			RG213, RG215, RG8	PE4430	$19.85				99
			RG214, RG9, RG225, RG393	PE4048	$22.33				1
			RG223, RG142, RG400, RG55	PE44788	$18.91				2
			RG58, RG141, RG303, LMR-195, PE-C195, PE-P195, .195 inch	PE4329	$15.12				3
			RG59*, RG62*, RG71	PE4432	$19.40				4
			RG8X, PE-C240, .240 inch, B7808A, LMR-240	PE4344	$15.05				5
		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE4934	$37.37				6
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45664	$13.44				7
			PE-SR401AL, PE-SR401FL, RG401	PE4376	$50.22				8
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE4140	$27.80				9
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44701	$21.21				10
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE45002	$38.36				11
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44700	$20.03				12
			SPO-500, SPP-500	TC-500-NM-LP	$9.86				13
			SPP-250-LLPL	PE45427	$27.76				14
			SPP-250-LLPL, SPO-250, SPF-250	TC-250-NM-LP	$12.32				15
			SPP-375-LLPL, SPO-375, SPF-375	TC-375-NM-LP	$12.32				16
			TFT-402, TFT-402-LF	TC-402-NM-LP	$14.30				17
		Threaded	VNA Test Cable	PE45505	$472.12				18
	Male, Bulkhead Mount								
Terminal		Solder	Solder Cup with .350 inch D Hole	PE4490	$47.10				19
			Solder Cup with .350 inch D Hole	PE4490BK	$46.22				20
			Solder Cup with .640 inch DD Hole	PE4489	$41.54				21

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

N Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	PRICE See Web for Volume Pricing			ROW
	Male, 4 Hole Flange Mount								
Terminal		Solder	Pin with .718 inch Hole Spacing	PE4491	$36.90				22
			Pin with .718 inch Hole Spacing	PE44653	$86.21				23
			Solder Cup with .718 inch Hole Spacing	PE4131	$19.12				24
	Male Right Angle								
Cable Connectors		Clamp/ Non-Solder Contact	1/2 inch Helical, 1/2 inch Superflexible, PE-1/2 Helical, PE-1/2SFHC	PE44554	$87.10		See Web for Volume Pricing		25
		Clamp/Solder	1/2 inch Annular, 1/2 inch Flexible, PE-1/2FAC	PE45358	$87.55				26
			PE-B400, PE-B405, PE-C400	PE4938	$28.56				27
			PE-P142LL	PE44816	$157.99				28
			PE-P160LL	PE45448	$142.68				29
			PE-P300LL	PE45225	$158.99				30
			PE-SR401AL, PE-SR401FL, RG401	PE4935	$33.12				31
			RG213, RG8, RG215, RG225, RG214, RG393	PE4136	$26.84				32
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4135	$24.86				33
		Crimp/ Non-Solder Contact	LMR-400, PE-C400, PE-B400, PE-B405	EZ-400-NMH-RA-X	$29.56				34
			LMR-600, PE-C600	EZ-600-NMH-RA-X	$30.80				35
		Crimp/Solder	LMR-195, PE-C195	TC-195-NMH-RA-D	$15.25				36
			PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE44524	$43.11				37
			PE-C200, LMR-200	PE44844	$55.81				38
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44525	$58.91				39
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44526	$44.66				40
			PE-C600, LMR-600, LMR-600-DB, .600 inch	PE44527	$64.27				41
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE44675	$37.02				42
			RG213, RG8	PE4482	$41.82				43
			RG214, RG9, RG225, RG393	PE4483	$54.03				44
			RG55, RG141, RG142, RG223, RG400	PE4484	$31.09				45
			RG58	PE4485	$27.56				46
		Solder/Solder	LMR-400, PE-C400, PE-B405	TC-400-NMH-RA-D	$21.56				47
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45665	$16.24				48
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44703	$26.34				49
			PE-SR402AL, PE-SR402FL, RG402	PE4936	$39.43				50
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405	PE4937	$28.55				51
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405	PE44702	$23.94				52
			SPO-250, SPF-250, SPP-250-LLPL	TC-250-NM-RA-LP	$14.78				53
			SPO-500, SPF-500	TC-SPO500-NM-RA-LP	$14.78				54
			SPP-250-LLPL	PE45428	$31.05				55
			TFT-402, TFT-402-LF	TC-402-NM-RA-LP	$15.95				56
	Female								
Cable Connectors		Clamp/ Non-Solder Contact	1/2 inch Helical, 1/2 inch Superflexible, PE-1/2 Helical, PE-1/2SFHC	PE44731	$50.09		See Web for Volume Pricing		57
			1/4 inch Superflexible, PE-1/4SFHC	PE44727	$64.59				58
			7/8 inch annular	PE45036	$68.71				59
			7/8 inch Helical	PE45203	$55.60				60
			PE-1/2FAC, 1/2 inch Flexible, 1/2 inch Annular	PE44737	$48.22				61
		Clamp/Solder	1/2 inch Annular	PE44565	$91.17				62
			PE-B400, PE-B405, PE-C400, LMR-400, .400 inch	PE4372	$34.79				63
			PE-C600	PE44350	$83.12				64
			PE-P300LL	PE45245	$111.50				65
			PE-SR401AL, PE-SR401FL, RG401	PE4439	$26.85				66
			PE-SR402AL, PE-SR402FL, RG402	PE4138	$23.40				67
			PE-SR405AL, PE-SR405FL, RG405	PE4130	$20.60				68
			RG14, RG217	PE4645	$77.21				69
			RG17, RG218, RG219	PE4646	$85.69				70
			RG174, RG316, RG188	PE4437	$22.48				71

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

N Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	PRICE See Web for Volume Pricing			ROW
	Female								
Cable Connectors		Clamp/Solder	RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4061	$20.38		See Web for Volume Pricing		72
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4072	$19.93				73
			RG59*, RG62*, RG71	PE4330	$20.14				74
		Clamp/Solder (Captive Contact)	RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4059	$33.89				75
		Crimp/Crimp	RG55, RG141, RG142, RG223, RG400	PE4134	$19.73				76
		Crimp/ Non-Solder Contact	LMR-600, PE-C600	EZ-600-NF-X	$24.64				77
		Crimp/Solder	LMR-400, PE-C400	TC-400-NF-X	$18.48				78
			PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE44532	$18.23				79
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44533	$19.30				80
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44534	$27.60				81
			PE-C600, LMR-600, LMR-600-DB, .600 inch	PE44535	$54.94				82
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4438	$26.27				83
			RG188-DS, RG316-DS	PE45172	$23.94				84
			RG213, RG8	PE4435	$18.17				85
			RG214, RG9, RG225, RG393	PE4191	$24.43				86
			RG223, RG142, RG400, RG55	PE44789	$23.59				87
			RG58	PE4436	$17.87				88
		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE4945	$43.25				89
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45666	$13.44				90
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44705	$27.88				91
			PE-SR402AL, PE-SR402FL, RG402	PE4652	$51.47				92
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405	PE4653	$34.29				93
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405	PE44704	$38.15				94
			SPO-375, SPF-375	TC-SPP375-NF-LP	$13.80				95
			SPP-250-LLPL	PE45426	$27.76				96
		Threaded	VNA Test Cable	PE45502	$421.62				97
PCB Mount		Solder	Thru Hole with .400 inch x .062 inch Hole Spacing	PE44396	$29.78				98
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	PE-B400, PE-B405, PE-C400 with .640 inch DD Hole	PE4943	$25.75		See Web for Volume Pricing		99
			PE-P142LL	PE44813	$106.68				1
			PE-P160LL	PE45447	$109.39				2
			PE-P300LL	PE44807	$125.56				3
			PE-SR401AL, PE-SR401FL, RG401 with .640 inch DD Hole	PE4942	$27.81				4
			PE-SR402AL, PE-SR402FL, RG402 with .640 inch DD Hole	PE4113	$21.61				5
			PE-SR405AL, PE-SR405FL, RG405, PE-SR405TN with .640 inch DD Hole	PE4443	$23.40				6
			RG174, RG316, RG188 with .640 inch DD Hole	PE4441	$24.91				7
			RG178 with .640 inch DD Hole	PE44633	$24.91				8
			RG188-DS, RG316-DS with .640 inch DD Hole	PE45173	$22.68				9
			RG214, RG213, RG393, RG8, RG225, RG11*, RG216*, RG144*, RG215, RG9 with .640 inch DD Hole	PE4223	$28.67				10
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, LMR-400, PE-C195, PE-P195 with .640 inch DD Hole	PE4114	$23.87				11
			RG59*, RG62* with .640 inch DD Hole	PE4297	$31.57				12

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

N Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, Bulkhead Mount								
Cable Connectors		Crimp/Crimp	RG55, RG142, RG223, RG400 with .640 inch DD Hole	PE4371	$23.67	$22.49	$21.30	$20.36	13
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch with .640 inch DD Hole	PE4440	$20.05	$19.05	$18.05	$17.24	14
		Crimp/ Non-Solder Contact	LMR-400, PE-C400, PE-B400, PE-B405	EZ-400-NF-BH	$23.00	$23.00	$23.00	$23.00	15
			LMR-600, PE-C600	EZ-600-NF-BH	$40.70	$40.70	$40.70	$40.70	16
		Crimp/Solder	.240 inch, RG8X, LMR-240, B7808A, LMR-240-DB, LMR-240-UF, PE-C240 with .640 inch DD Hole	PE44529	$20.28	$19.27	$18.25	$17.44	17
			.400 inch, LMR-400, LMR-400-DB, LMR-400-UF, PE-B405, PE-C400, PE-B400 with .640 inch DD Hole	PE44530	$27.50	$26.13	$24.75	$23.65	18
			LMR-200, PE-C200	PE45047	$25.80	$24.77	$23.99	$23.48	19
			LMR-240, PE-C240	TC-240-NF-BH-X	$24.02	$24.02	$24.02	$24.02	20
			PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch with .640 inch DD Hole	PE44528	$27.92	$26.52	$25.13	$24.01	21
			PE-C600, LMR-600 with .640 inch DD Hole	PE44531	$51.12	$48.56	$46.01	$43.96	22
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch with .640 inch DD Hole	PE4442	$30.34	$28.82	$27.31	$26.09	23
			RG188-DS, RG316-DS	PE44877	$32.94	$31.29	$29.65	$28.33	24
			RG213, RG8 with .640 inch DD Hole	PE4940	$34.41	$32.69	$30.97	$29.59	25
			RG214, RG9, RG225, RG393 with .640 inch DD Hole	PE4941	$21.44	$20.37	$19.30	$18.44	26
		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL with .640 inch DD Hole	PE4946	$38.08	$36.18	$34.27	$32.75	27
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45667	$13.44	$12.77	$12.10	$11.56	28
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402 with .640 inch DD Hole	PE44707	$24.59	$23.36	$22.13	$21.15	29
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402 with .640 inch DD Hole	PE4654	$42.05	$39.95	$37.85	$36.16	30
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44706	$26.34	$25.02	$23.71	$22.65	31
			PE-SR405AL, PE-SR405FL, RG405 with .640 inch DD Hole	PE4655	$39.02	$37.07	$35.12	$33.56	32
			SPP-250-LLPL	TC-SPP250-NF-BH-LP	$12.32	$12.32	$12.32	$12.32	33
			TFT-402, TFT-402-LF	TC-402-NF-BH-LP	$14.30	$14.30	$14.30	$14.30	34
PCB Mount		Solder	End Launch with .630 inch Diameter	PE44615	$34.80	$33.06	$31.32	$29.93	35
			Thru Hole with .640 inch DD Hole	PE44397	$53.01	$50.36	$47.71	$45.59	36
Terminal			Pin with .640 inch DD Hole	PE4139	$23.64	$22.46	$21.28	$20.33	37
			Solder Cup with .380 inch Diameter	PE4488	$16.32	$15.50	$14.69	$14.04	38
			Solder Cup with .640 inch DD Hole	PE4137	$34.71	$32.97	$31.24	$29.85	39
	Female, 2 Hole Flange Mount								
Terminal		Solder	Pin with 1.0 inch Hole Spacing	PE44079	$53.57	$50.89	$48.21	$46.07	40
			Solder Cup with 1.0 inch Hole Spacing	PE44077	$31.71	$30.12	$28.54	$27.27	41
	Female, 4 Hole Flange Mount								
Cable Connectors		Clamp/Solder	PE-SR401AL, PE-SR401FL, RG401 with .718 inch Hole Spacing	PE44071	$27.56	$26.18	$24.80	$23.70	42
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402 with .718 inch Hole Spacing	PE44072	$27.81	$26.42	$25.03	$23.92	43
			PE-SR405AL, PE-SR405FL, RG405 with .718 inch Hole Spacing	PE44073	$27.37	$26.00	$24.63	$23.54	44
			RG174, RG316, RG188 with .718 inch Hole Spacing	PE44070	$21.39	$20.32	$19.25	$18.40	45
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, LMR-400, PE-C195, PE-P195 with .718 inch Hole Spacing	PE4141	$21.87	$20.78	$19.68	$18.81	46
		Clamp/Solder (Captive Contact)	RG214, RG213, RG393, RG8, RG225, RG11*, RG216*, RG144*, RG215, RG9 with .718 inch Hole Spacing	PE4060	$28.93	$27.48	$26.04	$24.88	47
		Crimp/Solder	.195 inch, RG58, RG141, RG303, LMR-195, LMR-195-FR, PE-C195, PE-P195 with .718 inch Hole Spacing	PE44069	$27.08	$25.73	$24.37	$23.29	48
			RG213, RG8 with .718 inch Hole Spacing	PE44065	$25.06	$23.81	$22.55	$21.55	49
			RG214, RG9, RG225, RG393 with .718 inch Hole Spacing	PE44066	$28.69	$27.26	$25.82	$24.67	50
			RG316, RG174, LMR-100	PE45133	$23.40	$22.23	$21.06	$20.12	51
			RG55, RG141, RG142, RG223, RG400 with .718 inch Hole Spacing	PE44068	$27.34	$25.97	$24.61	$23.51	52

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

N Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, 4 Hole Flange Mount								
Terminal		Field Replaceable	Slotted Contact	PE44721	$35.80	$34.01	$32.22	$30.79	53
			Slotted Contact	PE44722	$36.83	$34.99	$33.15	$31.67	54
		Solder	Pin with .340 inch Hole Spacing	PE4355	$24.43	$23.21	$21.99	$21.01	55
			Pin with .500 inch Hole Spacing	PE4444	$24.66	$23.43	$22.19	$21.21	56
			Pin with .718 inch Hole Spacing	PE4328	$23.37	$22.20	$21.03	$20.10	57
			Solder Cup	PE45085	$21.13	$20.07	$19.02	$18.17	58
			Solder Cup with .718 inch Hole Spacing	PE4487	$62.93	$59.78	$56.64	$54.12	59
			Tab with .718 inch Hole Spacing	PE4492	$35.15	$33.39	$31.64	$30.23	60
	Female, Press-In								
Terminal		Solder	Pin with .500 inch Diameter	PE44074	$32.55	$30.92	$29.30	$27.99	61
			Solder Cup with .500 inch Diameter	PE44076	$20.22	$19.21	$18.20	$17.39	62
			Tab with .500 inch Diameter	PE44075	$21.05	$20.00	$18.95	$18.10	63
	Female Right Angle, Bulkhead Mount								
PCB Mount		Solder	Thru Hole with .596 inch D Hole	PE44398	$30.73	$29.19	$27.66	$26.43	64
	Female Right Angle, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .718 inch Hole Spacing	PE4486	$51.73	$49.14	$46.56	$44.49	65

Reverse Polarity N Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Crimp/Solder	PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44470	$39.06	$37.11	$35.15	$33.59	66
			RG213, RG8, RG215	PE44472	$38.65	$36.72	$34.79	$33.24	67
			RG214, RG393	PE44474	$32.09	$30.49	$28.88	$27.60	68
	Female								
Cable Connectors		Crimp/Solder	RG213, RG8	PE44478	$27.86	$26.47	$25.07	$23.96	69
			RG214, RG9, RG225, RG393	PE44477	$33.81	$32.12	$30.43	$29.08	70
			RG55, RG141, RG142, RG223, RG400	PE44475	$31.30	$29.74	$28.17	$26.92	71
			RG58	PE44476	$34.45	$32.73	$31.01	$29.63	72

N, 7mm, SC Torque Wrenches

Type	Bit Hex Size (in.)	Preset Torque (in.-lbs.)	Model No	1-9	10-24	25-49	50+	ROW
N, 7mm, SC	20 mm	14 in-lbs	PE5011-7	$318.02	$305.30	$295.76	$289.40	
		8.1 in-lbs	PE5019-5	$242.40	$230.28	$218.16	$208.46	
	3/4 inch	14 in-lbs	PE5019-4	$240.14	$228.13	$216.13	$206.52	
	13/16 inch	14 in-lbs	PE5019-8	$240.14	$228.13	$216.13	$206.52	

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

NEX10 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45672	$22.40	$21.28	$20.16	$19.26	73
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45668	$18.48	$17.56	$16.63	$15.89	74
			TFT-402, TFT-402-LF	TC-402-NX10M-LP	$20.79	$20.79	$20.79	$20.79	75
	Male Right Angle								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45669	$24.08	$22.88	$21.67	$20.71	76
			TFT-402, TFT-402-LF	TC-402-NX10M-RA-LP	$25.30	$25.30	$25.30	$25.30	77
	Female								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45670	$15.12	$14.36	$13.61	$13.00	78
	Female, Bulkhead Mount								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45671	$17.92	$17.02	$16.13	$15.41	79

NMO Mount Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Sexless								
Cable Connectors		Crimp/Solder	PE-C195, PE-P195, RG58, RG55, RG141, RG142, RG223, RG400, RG303, LMR-195	PE51021	$17.06	$16.21	$15.35	$14.67	80
			RG58, LMR-195	PE51167	$25.35	$24.08	$22.82	$21.80	81

QMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Crimp/Solder	LMR-200, PE-C200	PE45224	$16.40	$15.58	$14.76	$14.10	82
			PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE44503	$23.60	$22.42	$21.24	$20.30	83
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE44501	$32.09	$30.49	$28.88	$27.60	84
			RG55, RG142, RG223, RG400	PE44514	$22.57	$21.44	$20.31	$19.41	85
		Solder/ Non-Solder Contact	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44496	$50.28	$47.77	$45.25	$43.24	86
		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45682	$11.02	$10.47	$9.92	$9.48	87
			PE-SR405AL, PE-SR405FL, RG405	PE44495	$24.71	$23.47	$22.24	$21.25	88
			SPP-250-LLPL	PE45430	$23.35	$22.18	$21.02	$20.08	89
			TFT-402, TFT-402-LF	TC-402-QM-LP	$10.63	$10.63	$10.63	$10.63	90
	Male Right Angle								
Cable Connectors		Crimp/ Non-Solder Contact	LMR-240, PE-C240, LMR-240-UF	EZ-240-QM-RA-X	$19.50	$19.50	$19.50	$19.50	91
		Crimp/Solder	PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE44506	$31.30	$29.74	$28.17	$26.92	92
			RG174, RG316, RG188	PE45284	$26.46	$25.14	$23.81	$22.76	93
			RG316-DS, RG188-DS	PE44505	$34.32	$32.60	$30.89	$29.52	94
			RG55, RG142, RG223, RG400	PE44515	$32.91	$31.26	$29.62	$28.30	95
		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45683	$15.12	$14.36	$13.61	$13.00	96
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44498	$29.59	$28.11	$26.63	$25.45	97
			PE-SR405AL, PE-SR405FL, RG405	PE44497	$27.83	$26.44	$25.05	$23.93	98
			SPP-250-LLPL	PE45431	$25.69	$24.41	$23.12	$22.09	99
			TFT-402, TFT-402-LF	TC-402-QM-RA-LP	$15.95	$15.95	$15.95	$15.95	1

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

QMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female								
Cable Connectors		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45684	$10.83	$10.29	$9.75	$9.31	2
			SPP-250-LLPL	PE45429	$19.47	$18.50	$17.52	$16.74	3
PCB Mount		Solder	Surface Mount	PE44510	$26.26	$24.95	$23.63	$22.58	4
			Thru Hole	PE44512	$17.12	$16.26	$15.41	$14.72	5
	Female, Bulkhead Mount								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with .268 inch D Hole	PE44507	$26.75	$25.41	$24.08	$23.01	6
			RG316-DS, RG188-DS with .268 inch D Hole	PE44508	$20.79	$19.75	$18.71	$17.88	7
		Solder/Solder	PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45685	$13.44	$12.77	$12.10	$11.56	8
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402 with .268 inch D Hole	PE44500	$24.34	$23.12	$21.91	$20.93	9
			PE-SR405AL, PE-SR405FL, RG405 with .268 inch D Hole	PE45218	$31.84	$30.25	$28.66	$27.38	10
	Female Right Angle								
PCB Mount		Solder	Surface Mount	PE44511	$16.58	$15.92	$15.42	$15.09	11

QN Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Crimp/Solder	LMR-240, PE-C240	PE45222	$33.54	$32.20	$31.19	$30.52	12
			RG213, RG215	PE44597	$76.89	$73.81	$71.51	$69.97	13
			RG55, RG141, RG142, RG223, RG400	PE44978	$31.49	$29.92	$28.34	$27.08	14
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195	PE45071	$28.30	$27.17	$26.32	$25.75	15
		Solder/Solder	PE-SR402AL, PE-SR402FL, RG402	PE44599	$39.39	$37.42	$35.45	$33.88	16
	Male Right Angle								
Cable Connectors		Crimp/Solder	LMR-400, PE-C400, LMR-400-DB	PE45223	$54.37	$51.65	$48.93	$46.76	17
			PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE44601	$45.97	$43.67	$41.37	$39.53	18
			RG214, RG225	PE44603	$47.33	$44.96	$42.60	$40.70	19
			RG55, RG141, RG142, RG223, RG400	PE44600	$48.66	$46.23	$43.79	$41.85	20
		Solder/Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44604	$45.81	$43.52	$41.23	$39.40	21
	Female, Bulkhead Mount								
Cable Connectors		Crimp/Solder	RG213, RG215 with .500 inch Diameter	PE44607	$51.69	$49.11	$46.52	$44.45	22
			RG214, RG225 with .500 inch Diameter	PE44608	$103.37	$99.24	$96.13	$94.07	23
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup	PE44610	$73.22	$69.56	$65.90	$62.97	24

SC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-9	10-24	25-49	50+	ROW
	Male								
Cable Connectors		Clamp/Solder	RG213, RG214, RG8, RG9, RG225, RG393, RG215	PE4520	$188.79	$179.35	$169.91	$162.36	25
			RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE45479	$133.55	$126.87	$120.20	$114.85	26

*** Fits MIL-C-17 and equivalent cable versions only**

Connectors

See Our Website For Current Pricing & Real-Time Stock Availability!

SC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	PRICE See Web for Volume Pricing			ROW
	Male								
Cable Connectors		Crimp/Solder	RG214, RG9, RG225, RG393	PE4232	$66.95	See Web for Volume Pricing			27
			RG55, RG141, RG142, RG223, RG400	PE4231	$136.09				28
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG213, RG214, RG8, RG9, RG225, RG393, RG215	PE4979	$182.21				29
			RG58, RG55, RG141, RG142, RG223, RG400	PE4978	$152.60				30
	Female, Bulkhead Mount								
Terminal		Solder	Eyelet with .655 inch D Hole	PE4980	$40.20	See Web for Volume Pricing			31
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .718 inch Hole Spacing	PE4322	$45.95				32

SHV Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	PRICE 25-49	PRICE 50-99	PRICE 100 +	ROW
	Plug								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4498	$42.23	$40.12	$38.01	$36.32	33
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4316	$29.26	$27.80	$26.33	$25.16	34
			RG59*, RG62*, RG71	PE4100	$27.41	$26.04	$24.67	$23.57	35
			RG8, RG213, RG214	PE4333	$42.58	$40.45	$38.32	$36.62	36
		Crimp/Solder	RG213, RG8	PE4496	$39.27	$37.31	$35.34	$33.77	37
			RG214, RG9, RG225, RG393	PE4349	$44.74	$42.50	$40.27	$38.48	38
			RG55, RG142, RG223, RG400	PE4497	$39.63	$37.65	$35.67	$34.08	39
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4194	$50.24	$47.73	$45.22	$43.21	40
			RG59*, RG62*, RG71	PE4343	$44.89	$42.65	$40.40	$38.61	41
	Plug, Bulkhead Mount								
Terminal		Solder	Solder Cup with .350 inch D Hole	PE44118	$54.41	$51.69	$48.97	$46.79	42
	Jack, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188 with .480 inch D Hole	PE45556	$55.04	$52.29	$49.54	$47.33	43
			RG213, RG214, RG8, RG9, RG225, RG393, RG215 with .480 inch D Hole	PE44049	$70.81	$67.27	$63.73	$60.90	44
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, LMR-400, PE-C195, PE-P195 with .480 inch D Hole	PE44080	$54.04	$51.34	$48.64	$46.47	45
			RG59*, RG62*, RG71 with .480 inch D Hole	PE4315	$54.04	$51.34	$48.64	$46.47	46
Terminal		Solder	Solder Cup with .350 inch D Hole	PE4239	$25.80	$24.51	$23.22	$22.19	47
			Solder Cup with .350 inch D Hole	PE4500	$72.04	$68.44	$64.84	$61.95	48
			Solder Cup with .480 inch D Hole	PE4499	$36.07	$34.27	$32.46	$31.02	49
	Jack, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .500 inch Hole Spacing	PE4501	$41.25	$39.19	$37.13	$35.48	50

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
PCB Mount		Clamp	Vertical Launch	PE45460	$41.00	$38.95	$36.90	$35.26	51
			Vertical Launch	PE45461	$43.42	$41.68	$40.38	$39.51	52
Cable Connectors		Clamp/Solder	PE-P142LL	PE44826	$43.17	$41.01	$38.85	$37.13	53
			PE-P160LL	PE45440	$85.22	$80.96	$76.70	$73.29	54
			PE-P300LL	PE44808	$67.04	$63.69	$60.34	$57.65	55
			PE-P300LL	PE45042	$70.35	$70.35	$70.35	$70.35	56
			PE-SR401AL, PE-SR401FL, RG401	PE4403	$47.04	$44.69	$42.34	$40.45	57
			RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE4026	$32.40	$30.78	$29.16	$27.86	58
			RG178, RG196	PE4214	$58.74	$55.80	$52.87	$50.52	59
			RG180, RG195, PE-B150	PE4399	$26.62	$25.29	$23.96	$22.89	60
			RG188-DS, RG316-DS	PE4400	$34.60	$32.87	$31.14	$29.76	61
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4332	$92.20	$87.59	$82.98	$79.29	62
			RG316, RG174, LMR-100	PE45142	$16.67	$15.84	$15.00	$14.34	63
			RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE4027	$31.32	$29.75	$28.19	$26.94	64
			RG58, RG303, LMR-195, PE-P195	PE45140	$26.24	$24.93	$23.62	$22.57	65
		Crimp/Crimp	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4003	$12.43	$11.81	$11.19	$10.69	66
		Crimp/ Non-Solder Contact	LMR-240, PE-C240	EZ-240-SM-X	$10.17	$10.17	$10.17	$10.17	67
		Crimp/Solder	LMR-195, PE-C195	TC-195-SM-SS-X	$15.25	$15.25	$15.25	$15.25	68
			LMR-200, PE-C200	TC-200-SM-SS-X	$14.00	$14.00	$14.00	$14.00	69
			LMR-200, PE-C200	PE45040	$8.60	$8.26	$8.00	$7.83	70
			LMR-240, PE-C240, LMR-240-UF	TC-240-SM-SS-X	$10.71	$10.71	$10.71	$10.71	71
			LMR-400, PE-C400	TC-400-SM-X	$14.78	$14.78	$14.78	$14.78	72
			PE-B150, RG180, RG195	PE4578	$27.75	$26.36	$24.98	$23.87	73
			PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE44460	$83.53	$80.19	$77.68	$76.01	74
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44637	$19.92	$18.92	$17.93	$17.13	75
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44668	$31.83	$30.24	$28.65	$27.37	76
			PE-P195	PE44203	$19.99	$18.99	$17.99	$17.19	77
			RG142, RG223, RG400, RG55	PE44461	$67.13	$64.44	$62.43	$61.09	78
			RG174, RG316, RG188	PE45145	$13.32	$12.65	$11.99	$11.46	79
			RG178, RG196	PE4398	$22.43	$21.31	$20.19	$19.29	80
			RG188-DS, RG316-DS	PE4401	$6.88	$6.54	$6.19	$5.92	81
			RG55, RG142, RG223, RG400, RG141	PE4008	$14.24	$13.53	$12.82	$12.25	82
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4215	$13.76	$13.07	$12.38	$11.83	83
			RG59*, RG62*, RG71	PE4294	$28.93	$27.48	$26.04	$24.88	84
		Crimp/Solder (Captive Contact)	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4589	$21.18	$20.12	$19.06	$18.21	85
			RG55, RG141, RG142, RG223, RG400	PE4576	$32.08	$30.48	$28.87	$27.59	86
			RG58	PE4577	$27.15	$25.79	$24.44	$23.35	87
		Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44691	$10.15	$9.64	$9.14	$8.73	88
			RG405, RG405 Tinned	PE45481	$42.95	$40.80	$38.66	$36.94	89
			RG405, RG405 Tinned, PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN	PE45480	$42.95	$40.80	$38.66	$36.94	90
		Solder (Without Contact)	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE4007	$11.80	$11.21	$10.62	$10.15	91
		Solder/Solder	PE-020SR	PE4918	$50.69	$48.16	$45.62	$43.59	92
			PE-034SR	PE4917	$88.35	$83.93	$79.52	$75.98	93
			PE-047SR, PE-SR047AL, PE-SR047FL	PE44757	$38.79	$36.07	$33.36	$31.03	94
			PE-047SR, PE-SR047AL, PE-SR047FL	PE4404	$32.70	$31.07	$29.43	$28.12	95
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45678	$7.98	$7.58	$7.18	$6.86	96
			PE-SR401AL, PE-SR401FL, RG401	PE4907	$48.96	$46.51	$44.06	$42.11	97

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	PRICE See Web for Volume Pricing			ROW
	Male								
Cable Connectors		Solder/Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE4112	$12.20		See Web for Volume Pricing		98
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44690	$11.42				99
			PE-SR405AL, PE-SR405FL, RG405	PE4005	$9.07				1
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4036	$16.48				2
			RG178, RG196	PE4213	$21.12				3
			RG188-DS, RG316-DS	PE4402	$19.11				4
			RG405, PE-SR405FL, PE-SR405FLJ	PE45135	$10.64				5
			RG58, RG55, RG142, RG223, RG400	PE4037	$17.63				6
			SPP-250-LLPL	PE45543	$16.02				7
			TFT-402, TFT-402-LF	TC-402-SM-LP	$7.98				8
		Solder/Solder (Captive Contact)	RG174, RG316, RG188	PE4590	$19.38				9
			RG58, RG55, RG142, RG223, RG400	PE4587	$24.58				10
PCB Mount		Solder	.042 inch End Launch	PE44210	$37.56				11
			.062 inch End Launch	PE4913	$36.91				12
			.062 inch End Launch	PE4912	$35.55				13
			Thru Hole with .200 inch x .067 inch Hole Spacing	PE4525	$24.96				14
	Male, Bulkhead Mount								
Terminal		Solder	Solder Cup with .235 inch D Hole	PE4354	$23.10				15
			Stub with .250 inch Diameter	PE4531	$44.48				16
	Male, 2 Hole Flange Mount								
Field Replaceable		Field Replaceable	.036 inch Pin	PE44032	$21.34		See Web for Volume Pricing		17
Terminal		Solder	Solder Cup	PE45139	$11.56				18
			Solder Cup with .481 inch Hole Spacing	PE4125	$33.13				19
			Stub with .481 inch Hole Spacing	PE4127	$16.61				20
	Male, 4 Hole Flange Mount								
Field Replaceable		Field Replaceable	.012 inch Pin	PE44018	$30.37				21
			.012 inch Pin	PE44005	$41.13				22
			.015 inch Pin	PE44019	$50.34				23
			.018 inch Pin	PE44007	$26.24				24
			.020 inch Pin	PE44008	$43.55				25
			.020 inch Pin	PE44021	$27.27				26
			.036 inch Pin	PE44009	$26.75				27
Terminal		Solder	Pin with .340 inch Hole Spacing	PE4541	$59.29				28
			Solder Cup with .340 inch Hole Spacing	PE45204	$55.89				29
			Stub with .340 inch Hole Spacing	PE4126	$32.56				30
	Male Right Angle								
Cable Connectors		Clamp/Solder	PE-P142LL	PE44817	$133.42		See Web for Volume Pricing		31
			PE-P160LL	PE45442	$120.49				32
			PE-P300LL	PE45041	$134.77				33
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44996	$105.75				34
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE4028	$37.92				35
			RG178, RG196	PE4108	$23.79				36
			RG180, RG195	PE4579	$28.26				37
			RG188-DS, RG316-DS	PE4407	$57.23				38
			RG58, RG55, RG141, RG142, RG223, RG303, RG400, LMR-195, PE-C195	PE45048	$55.13				39
		Crimp/ Non-Solder Contact	LMR-240	EZ-240-SM-RA-X	$13.55				40
		Crimp/Solder	PE-B150, RG180, RG195	PE4580	$27.52				41
			PE-C200, LMR-200	PE45546	$25.83				42
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44638	$31.57				43

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male Right Angle								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4009	$22.97	$21.82	$20.67	$19.75	44
			RG178, RG196	PE4296	$31.54	$29.96	$28.39	$27.12	45
			RG188-DS, RG316-DS	PE4408	$21.89	$20.80	$19.70	$18.83	46
			RG316, RG174, RG188	PE45144	$22.49	$20.92	$19.34	$17.99	47
			RG55, RG142, RG223, RG400, RG141	PE4002	$21.14	$20.08	$19.03	$18.18	48
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4405	$13.46	$12.79	$12.11	$11.58	49
			RG59*, RG62*, RG71	PE4327	$39.04	$37.09	$35.14	$33.57	50
		Solder/Solder	PE-020SR	PE4920	$73.13	$69.47	$65.82	$62.89	51
			PE-034SR	PE4919	$65.94	$62.64	$59.35	$56.71	52
			PE-047SR, PE-SR047AL, PE-SR047FL	PE45282	$66.66	$63.33	$59.99	$57.33	53
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45679	$9.12	$8.66	$8.21	$7.84	54
			PE-SR401AL, PE-SR401FL, RG401	PE4932	$66.99	$63.64	$60.29	$57.61	55
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE4083	$24.71	$23.47	$22.24	$21.25	56
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44693	$15.57	$14.79	$14.01	$13.39	57
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44692	$13.86	$13.17	$12.47	$11.92	58
			PE-SR405AL, PE-SR405FL, RG405	PE4025	$36.54	$34.71	$32.89	$31.42	59
			RG178, RG196	PE4406	$27.37	$26.00	$24.63	$23.54	60
			RG188-DS, RG316-DS	PE4409	$27.41	$26.04	$24.67	$23.57	61
			RG316, RG174, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4038	$22.80	$21.66	$20.52	$19.61	62
			RG58, RG55, RG142, RG223, RG400	PE4039	$20.69	$19.66	$18.62	$17.79	63
			SPP-250-LLPL	PE45434	$17.13	$16.27	$15.42	$14.73	64
	Female								
Cable Connectors		Clamp/Solder	PE-P142LL	PE44814	$75.48	$71.71	$67.93	$64.91	65
			RG178, RG196	PE4591	$32.54	$30.91	$29.29	$27.98	66
			RG188-DS, RG316-DS	PE4415	$36.52	$34.69	$32.87	$31.41	67
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393	PE4411	$69.11	$65.65	$62.20	$59.43	68
			RG316, RG174, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE4030	$37.00	$35.15	$33.30	$31.82	69
			RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE4031	$49.40	$46.93	$44.46	$42.48	70
		Crimp/Solder	PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44639	$27.41	$26.04	$24.67	$23.57	71
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44669	$52.92	$50.27	$47.63	$45.51	72
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE4414	$22.67	$21.54	$20.40	$19.50	73
			RG178, RG196	PE4325	$34.59	$32.86	$31.13	$29.75	74
			RG188-DS, RG316-DS	PE4416	$22.48	$21.36	$20.23	$19.33	75
			RG316, RG174, LMR-100, RG188, PE-B100, PE-C100, 0.100 inch	PE45137	$9.40	$8.93	$8.46	$8.08	76
			RG55, RG142, RG223	PE4412	$17.55	$16.67	$15.80	$15.09	77
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195	PE4413	$20.05	$19.05	$18.05	$17.24	78
			RG59*, RG62*	PE4326	$31.42	$29.85	$28.28	$27.02	79
		Solder/Solder	PE-020SR	PE4922	$71.82	$68.23	$64.64	$61.77	80
			PE-034SR	PE4921	$65.94	$62.64	$59.35	$56.71	81
			PE-047SR, PE-SR047AL, PE-SR047FL	PE4418	$38.96	$37.01	$35.06	$33.51	82
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45680	$8.55	$8.12	$7.70	$7.35	83
			PE-SR401AL, PE-SR401FL, RG401	PE4930	$33.24	$31.58	$29.92	$28.59	84
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE4115	$20.13	$19.12	$18.12	$17.31	85
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44695	$13.85	$13.16	$12.47	$11.91	86
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44694	$9.72	$9.23	$8.75	$8.36	87
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405	PE4116	$26.12	$24.81	$23.51	$22.46	88
			RG178, RG196	PE4592	$28.56	$27.13	$25.70	$24.56	89
			RG188-DS, RG316-DS	PE4417	$17.28	$16.42	$15.55	$14.86	90
			RG316, RG174, RG188	PE4040	$17.86	$16.97	$16.07	$15.36	91
			RG58, RG55, RG142, RG223, RG400	PE4041	$19.27	$18.31	$17.34	$16.57	92
			SPP-250-LLPL	PE45432	$16.83	$15.99	$15.15	$14.47	93
PCB Mount		Clamp	Vertical Launch	PE45459	$40.57	$38.54	$36.51	$34.89	94
			Vertical Launch	PE45458	$40.57	$38.54	$36.51	$34.89	95

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female								
PCB Mount		Clamp/Solder (Captive Contact)	End Launch	PE45466	$55.11	$52.35	$49.60	$47.39	96
			End Launch	PE45463	$57.24	$54.38	$51.52	$49.23	97
			End Launch	PE45462	$57.24	$54.38	$51.52	$49.23	98
			End Launch	PE45464	$57.24	$54.38	$51.52	$49.23	99
			End Launch	PE45465	$57.24	$54.38	$51.52	$49.23	1
		Solder	.031 inch End Launch	PE44206	$23.42	$22.25	$21.08	$20.14	2
			.042 inch End Launch	PE44207	$30.14	$28.63	$27.13	$25.92	3
			.042 inch End Launch	PE44204	$28.25	$26.84	$25.43	$24.30	4
			.047 inch End Launch	PE44205	$32.29	$30.68	$29.06	$27.77	5
			.047 inch End Launch	PE44208	$30.79	$29.25	$27.71	$26.48	6
			.062 inch End Launch	PE4542	$21.39	$20.32	$19.25	$18.40	7
			.062 inch End Launch	PE4543	$22.88	$21.74	$20.59	$19.68	8
			.078 inch End Launch	PE44614	$38.48	$36.56	$34.63	$33.09	9
			End Launch	PE44235	$26.18	$24.87	$23.56	$22.51	10
			Surface Mount	PE4910	$20.38	$19.36	$18.34	$17.53	11
			Thru Hole	PE4117	$16.59	$15.76	$14.93	$14.27	12
			Thru Hole with .200 inch x .067 inch Hole Spacing	PE44827	$12.52	$11.89	$11.27	$10.77	13
		Solder/Solder (Captive Contact)	1/16 inch Stripline	PE4534	$49.16	$46.70	$44.24	$42.28	14
			1/8 inch Stripline	PE4190	$48.89	$46.45	$44.00	$42.05	15
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	PE-P160LL	PE45441	$101.29	$96.23	$91.16	$87.11	16
			RG178, RG196 with .235 inch D Hole	PE4421	$42.81	$40.67	$38.53	$36.82	17
			RG188-DS, RG316-DS with .235 inch D Hole	PE4424	$45.74	$43.45	$41.17	$39.34	18
			RG316, RG174, RG188, PE-B100, PE-C100, .100 inch, LMR-100 with .235 inch D Hole	PE4032	$40.88	$38.84	$36.79	$35.16	19
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, LMR-400, PE-C195, PE-P195 with .235 inch D Hole	PE4033	$44.02	$41.82	$39.62	$37.86	20
		Crimp/Solder	RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100 with .235 inch D Hole	PE44643	$22.95	$21.80	$20.66	$19.74	21
			RG178, RG196 with .235 inch D Hole	PE4422	$32.31	$30.69	$29.08	$27.79	22
			RG178, RG196 with .235 inch D Hole	PE45292	$19.75	$18.76	$17.78	$16.99	23
			RG188-DS, RG316-DS with .235 inch D Hole	PE4425	$25.52	$24.24	$22.97	$21.95	24
			RG316, RG174, LMR-100	PE45136	$17.76	$16.87	$15.98	$15.27	25
			RG316, RG174, RG188, PE-B100, PE-C100, .100 inch, LMR-100 with .235 inch D Hole	PE4427	$20.21	$19.20	$18.19	$17.38	26
			RG55, RG142, RG223, RG141 with .235 inch D Hole	PE4419	$24.71	$23.47	$22.24	$21.25	27
			RG58 with .235 inch D Hole	PE4420	$21.89	$20.80	$19.70	$18.83	28
			RG58, RG303, LMR-195	PE45138	$12.78	$12.14	$11.50	$10.99	29
			RG58, RG303, LMR-195, PE-P195	PE45141	$14.40	$13.68	$12.96	$12.38	30
			RG59*, RG62*, RG71 with .235 inch D Hole	PE4914	$29.08	$27.63	$26.17	$25.01	31
		Solder/Solder	PE-020SR with .235 inch D Hole	PE4924	$72.32	$68.70	$65.09	$62.20	32
			PE-034SR with .235 inch D Hole	PE4923	$75.19	$71.43	$67.67	$64.66	33
			PE-1/4SFHC, SPP-250-LLPL, SPO-250, SPF-250	PE45681	$11.40	$10.83	$10.26	$9.80	34
			PE-SR401AL, PE-SR401FL, RG401 with .235 inch D Hole	PE4931	$65.11	$61.85	$58.60	$55.99	35
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44697	$12.81	$12.17	$11.53	$11.02	36
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402 with .235 inch D Hole	PE45554	$18.94	$17.99	$17.05	$16.29	37
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405 with .235 inch D Hole	PE44696	$14.25	$13.54	$12.83	$12.26	38
			PE-SR405AL, PE-SR405FL, RG405 with .235 inch D Hole	PE4119	$17.29	$16.43	$15.56	$14.87	39
			RG178, RG196 with .235 inch D Hole	PE4423	$27.76	$26.37	$24.98	$23.87	40
			RG188-DS, RG316-DS with .235 inch D Hole	PE4426	$23.40	$22.23	$21.06	$20.12	41
			RG316, RG174, RG188 with .235 inch D Hole	PE4188	$20.33	$19.31	$18.30	$17.48	42
			RG58, RG55, RG142, RG223 with .235 inch D Hole	PE4353	$21.61	$20.53	$19.45	$18.58	43
PCB Mount		Solder	.042 inch End Launch with .250 inch Diameter	PE44213	$27.90	$26.51	$25.11	$23.99	44
			.042 inch End Launch with .250 inch Diameter	PE44211	$30.62	$29.09	$27.56	$26.33	45
			.062 inch End Launch with .250 inch Diameter	PE44212	$27.83	$26.44	$25.05	$23.93	46
			.062 inch End Launch with .250 inch Diameter	PE44214	$29.51	$28.03	$26.56	$25.38	47
			End Launch	PE45134	$28.99	$27.54	$26.09	$24.93	48
			Thru Hole with .235 inch D Hole	PE4524	$22.18	$21.07	$19.96	$19.07	49
Terminal			Pin	PE45547	$18.24	$17.33	$16.42	$15.69	50
			Solder Cup with .235 inch D Hole	PE4529	$54.66	$51.93	$49.19	$47.01	51
			Solder Cup with .235 inch D Hole	PE4219	$17.16	$16.30	$15.44	$14.76	52

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, Bulkhead Mount								
Terminal		Solder	Solder Cup with .235 inch D Hole	PE4101	$21.14	$20.08	$19.03	$18.18	53
			Solder Cup with .350 inch D Hole	PE4536	$50.34	$47.82	$45.31	$43.29	54
			Solder Cup with .250 inch Diameter	PE4549	$32.85	$31.21	$29.57	$28.25	55
			Stub with .235 inch D Hole	PE4528	$49.59	$47.11	$44.63	$42.65	56
			Stub with .250 inch Diameter	PE4530	$34.93	$33.18	$31.44	$30.04	57
			Stub with .250 inch Diameter	PE4532	$31.72	$30.13	$28.55	$27.28	58
			Stub with .250 inch Diameter	PE4189	$18.84	$17.90	$16.96	$16.20	59
			Stub with .250 inch Diameter	PE44591	$33.38	$31.71	$30.04	$28.71	60
	Female, 2 Hole Flange Mount								
Field Replaceable		Field Replaceable	0.009 inch Pin	PE45578	$27.19	$25.83	$24.47	$23.38	61
			0.009 inch Pin	PE45572	$31.35	$29.78	$28.22	$26.96	62
			0.009 inch Pin with .481 inch Hole Spacing	PE45584	$26.03	$24.73	$23.43	$22.39	63
			0.012 inch Pin	PE45579	$21.76	$20.67	$19.58	$18.71	64
			0.012 inch Pin	PE45573	$25.78	$24.49	$23.20	$22.17	65
			.012 inch Pin	PE45217	$32.97	$31.32	$29.67	$28.35	66
			0.012 inch Pin with .481 inch Hole Spacing	PE45585	$20.84	$19.80	$18.76	$17.92	67
			0.015 inch Pin	PE45574	$27.06	$25.71	$24.35	$23.27	68
			0.015 inch Pin	PE45580	$22.83	$21.69	$20.55	$19.63	69
			.015 inch Pin	PE44024	$36.92	$35.07	$33.23	$31.75	70
			0.015 inch Pin with .481 inch Hole Spacing	PE45586	$20.92	$19.87	$18.83	$17.99	71
			0.018 inch Pin	PE45575	$27.59	$26.21	$24.83	$23.73	72
			0.018 inch Pin	PE45581	$23.93	$22.73	$21.54	$20.58	73
			0.018 inch Pin with .481 inch Hole Spacing	PE45587	$21.68	$20.60	$19.51	$18.64	74
			0.02 inch Pin	PE45582	$23.93	$22.73	$21.54	$20.58	75
			0.02 inch Pin	PE45576	$24.62	$23.39	$22.16	$21.17	76
			0.02 inch Pin with .481 inch Hole Spacing	PE45588	$22.91	$21.76	$20.62	$19.70	77
			0.036 inch Pin	PE45583	$27.50	$26.13	$24.75	$23.65	78
			0.036 inch Pin	PE45577	$27.56	$26.18	$24.80	$23.70	79
			.036 inch Pin	PE45055	$32.32	$30.70	$29.09	$27.80	80
			0.036 inch Pin with .481 inch Hole Spacing	PE45589	$20.86	$19.82	$18.77	$17.94	81
Terminal		Compression	Stub with .481 inch Hole Spacing	PE44340	$68.31	$64.89	$61.48	$58.75	82
		Solder	Solder Cup with .481 inch Hole Spacing	PE4004	$19.39	$18.42	$17.45	$16.68	83
			Solder Cup with .481 inch Hole Spacing	PE44341	$66.49	$63.17	$59.84	$57.18	84
			Stub	PE45067	$16.11	$15.30	$14.50	$13.85	85
			Stub	PE45039	$16.68	$16.01	$15.51	$15.18	86
			Stub with .481 inch Hole Spacing	PE4128	$24.02	$22.82	$21.62	$20.66	87
			Stub with .481 inch Hole Spacing	PE4128-SF	$20.49	$19.47	$18.44	$17.62	88
			Tab with .481 inch Hole Spacing	PE4370	$27.35	$25.98	$24.62	$23.52	89
Cable Connectors		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL with .481 inch Hole Spacing	PE4547	$30.59	$29.06	$27.53	$26.31	90
			PE-SR402AL, PE-SR402FL, RG402 with .481 inch Hole Spacing	PE4196	$33.45	$31.78	$30.11	$28.77	91
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405 with .481 inch Hole Spacing	PE4197	$27.66	$26.28	$24.89	$23.79	92
	Female, 4 Hole Flange Mount								
Cable Connectors		Clamp/Solder	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100A-FR, PE-C100, PE-B100 with .340 inch Hole Spacing	PE4034	$72.32	$68.70	$65.09	$62.20	93
			RG58, RG55, RG141, RG142, RG223, RG400 with .340 inch Hole Spacing	PE4035	$64.58	$61.35	$58.12	$55.54	94
		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL with .340 inch Hole Spacing	PE4548	$87.38	$83.01	$78.64	$75.15	95
			RG402, RG402 Tinned, PE-SR402FL, PE-SR402AL, PE-SR402FLJ, PE-SR402TN with .340 inch Hole Spacing	PE4121	$41.64	$39.56	$37.48	$35.81	96
			RG405, RG405 Tinned, PE-SR405FL, PE-SR405AL, PE-SR405FLJ, PE-SR405TN	PE44998	$34.77	$33.03	$31.29	$29.90	97
Field Replaceable		Field Replaceable	0.009 inch Pin	PE45566	$36.87	$35.03	$33.18	$31.71	98
			0.009 inch Pin	PE45560	$35.06	$33.31	$31.55	$30.15	99
			0.012 inch Pin	PE45567	$29.49	$28.02	$26.54	$25.36	1
			0.012 inch Pin	PE45561	$28.05	$26.65	$25.25	$24.12	2
			.012 inch Pin	PE44010	$40.63	$38.60	$36.57	$34.94	3
			.012 inch Pin	PE44000	$42.53	$40.40	$38.28	$36.58	4
			0.015 inch Pin	PE45562	$28.67	$27.24	$25.80	$24.66	5
			0.015 inch Pin	PE45568	$30.97	$29.42	$27.87	$26.63	6

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, 4 Hole Flange Mount								
Field Replaceable		Field Replaceable	.015 inch Pin	PE44001	$39.38	$37.41	$35.44	$33.87	7
			.015 inch Pin	PE45216	$26.52	$25.19	$23.87	$22.81	8
			0.018 inch Pin	PE45569	$32.44	$30.82	$29.20	$27.90	9
			0.018 inch Pin	PE45563	$30.86	$29.32	$27.77	$26.54	10
			0.02 inch Pin	PE45570	$32.44	$30.82	$29.20	$27.90	11
			0.02 inch Pin	PE45564	$35.44	$33.67	$31.90	$30.48	12
			.020 inch Pin	PE45215	$23.66	$22.48	$21.29	$20.35	13
			.020 inch Pin	PE44003	$39.78	$37.79	$35.80	$34.21	14
			0.036 inch Pin	PE45565	$32.26	$30.65	$29.03	$27.74	15
			0.036 inch Pin	PE45571	$33.91	$32.21	$30.52	$29.16	16
			.036 inch Pin	PE44004	$42.53	$40.40	$38.28	$36.58	17
			.036 inch Pin	PE45053	$35.40	$33.63	$31.86	$30.44	18
Terminal		Solder	Pin with .340 inch Hole Spacing	PE4540	$54.67	$51.94	$49.20	$47.02	19
			Pin with .340 inch Hole Spacing	PE4217	$28.25	$26.84	$25.43	$24.30	20
			Pin with .375 inch x .500 inch Hole Spacing	PE4538	$46.65	$44.32	$41.99	$40.12	21
			Solder Cup with .340 inch Hole Spacing	PE4537	$35.78	$33.99	$32.20	$30.77	22
			Solder Cup with .340 inch Hole Spacing	PE4000	$25.56	$24.28	$23.00	$21.98	23
			Solder Cup with .500 inch Hole Spacing	PE4527	$30.62	$29.09	$27.56	$26.33	24
			Solder Cup with .718 inch Hole Spacing	PE4218	$31.53	$29.95	$28.38	$27.12	25
			Stub	PE4111	$37.47	$35.60	$33.72	$32.22	26
			Stub with .340 inch Hole Spacing	PE4099	$19.92	$18.92	$17.93	$17.13	27
			Stub with .500 inch Hole Spacing	PE4533	$29.27	$27.81	$26.34	$25.17	28
			Tab with .340 inch Hole Spacing	PE4186	$23.95	$22.75	$21.56	$20.60	29
			Tab with .375 inch x .500 inch Hole Spacing	PE4539	$35.78	$33.99	$32.20	$30.77	30
	Female, Press-In								
Terminal		Solder	Tab with .200 inch Diameter	PE44241	$35.71	$33.92	$32.14	$30.71	31
			Tab with .200 inch Diameter	PE44240	$31.96	$30.36	$28.76	$27.49	32
	Female Right Angle								
PCB Mount		Solder	Surface Mount	PE4911	$31.42	$29.85	$28.28	$27.02	33
	Female Right Angle, Bulkhead Mount								
PCB Mount		Solder	Thru Hole with .235 inch D Hole	PE4545	$33.66	$31.98	$30.29	$28.95	34
Terminal			Solder Cup with .235 inch D Hole	PE4300	$59.11	$56.15	$53.20	$50.83	35
	Female Right Angle, 2 Hole Flange Mount								
Terminal		Solder	Pin with .481 inch Hole Spacing	PE44237	$59.50	$56.53	$53.55	$51.17	36
			Pin with .481 inch Hole Spacing	PE44238	$54.84	$52.10	$49.36	$47.16	37
			Pin with .481 inch Hole Spacing	PE44239	$57.15	$54.29	$51.44	$49.15	38
			Pin with .481 inch Hole Spacing	PE44593	$55.88	$53.09	$50.29	$48.06	39
	Female Right Angle, 4 Hole Flange Mount								
Field Replaceable		Field Replaceable	.012 inch Pin	PE44015	$63.71	$60.52	$57.34	$54.79	40
Terminal		Solder	Pin with .340 inch Hole Spacing	PE44236	$34.69	$32.96	$31.22	$29.83	41
			Solder Cup with .340 inch Hole Spacing	PE4123	$42.58	$40.45	$38.32	$36.62	42

Reverse Polarity SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE4770	$41.00	$38.95	$36.90	$35.26	43
			RG178, RG196	PE4773	$14.49	$13.77	$13.04	$12.46	44

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

Reverse Polarity SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE4766	$37.50	$35.63	$33.75	$32.25	45
		Crimp/Solder	PE-B150, RG180, RG195	PE4777	$17.11	$16.25	$15.40	$14.71	46
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44664	$27.95	$26.55	$25.16	$24.04	47
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44666	$32.97	$31.32	$29.67	$28.35	48
			RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE4771	$23.18	$22.02	$20.86	$19.93	49
			RG188-DS, RG316-DS	PE45183	$21.09	$20.04	$18.98	$18.14	50
			RG55, RG141, RG142, RG223, RG400	PE4767	$24.40	$23.18	$21.96	$20.98	51
			RG58	PE4769	$24.97	$23.72	$22.47	$21.47	52
			RG178, RG196	PE45008	$47.80	$45.41	$43.02	$41.11	53
		Solder/Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44724	$23.66	$22.48	$21.29	$20.35	54
			RG174, RG316, RG188	PE4772	$23.07	$21.92	$20.76	$19.84	55
			RG178, RG196	PE4775	$28.67	$27.52	$26.66	$26.09	56
			RG58, RG55, RG141, RG142, RG223, RG400	PE4768	$24.91	$23.66	$22.42	$21.42	57
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188	PE4784	$62.14	$59.03	$55.93	$53.44	58
			RG58, RG55, RG141, RG142, RG223, RG400	PE4780	$45.27	$43.01	$40.74	$38.93	59
		Crimp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE4785	$62.70	$59.57	$56.43	$53.92	60
			RG178, RG196	PE4788	$41.92	$39.82	$37.73	$36.05	61
			RG188-DS, RG316-DS	PE45185	$47.71	$45.32	$42.94	$41.03	62
			RG55, RG142, RG223, RG400	PE44975	$43.96	$41.76	$39.56	$37.81	63
			RG58, RG141, PE-C195, PE-P195	PE45012	$37.89	$36.00	$34.10	$32.59	64
		Solder/Solder	PE-SR402AL, PE-SR402FL, RG402	PE4790	$50.34	$47.82	$45.31	$43.29	65
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE4791	$53.09	$50.44	$47.78	$45.66	66
			RG174, RG316, RG188	PE4786	$42.19	$40.08	$37.97	$36.28	67
			RG58, RG55, RG141, RG142, RG223, RG400	PE4782	$42.19	$40.08	$37.97	$36.28	68
	Female								
Cable Connectors		Clamp/Solder	RG178, RG196	PE4850	$13.72	$13.17	$12.76	$12.49	69
			RG55, RG58, RG141, RG142, RG223, RG303, RG400, PE-C195, PE-P195, LMR-195	PE4792	$36.20	$34.39	$32.58	$31.13	70
		Crimp/Crimp	LMR-400, PE-C400, PE-B400, PE-B405	PE45397	$7.10	$6.75	$6.39	$6.11	71
		Crimp/Solder	PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44665	$29.74	$28.25	$26.77	$25.58	72
			RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100, RG179	PE4797	$34.54	$32.81	$31.09	$29.70	73
			RG178, RG196	PE4799	$33.79	$32.10	$30.41	$29.06	74
			RG188-DS, RG316-DS	PE45186	$31.20	$29.64	$28.08	$26.83	75
			RG55, RG141, RG142, RG223, RG400	PE4793	$37.18	$35.32	$33.46	$31.97	76
			RG58	PE4795	$29.28	$27.82	$26.35	$25.18	77
		Solder/Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44723	$29.09	$27.64	$26.18	$25.02	78
			PE-SR402AL, PE-SR402FL, RG402	PE4852	$34.43	$32.71	$30.99	$29.61	79
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE4853	$19.10	$18.15	$17.19	$16.43	80
			RG174, RG316, RG188	PE4798	$29.85	$28.36	$26.87	$25.67	81
			RG178, RG196	PE4851	$26.03	$24.73	$23.43	$22.39	82
			RG58, RG55, RG141, RG142, RG223, RG400	PE4794	$27.84	$26.45	$25.06	$23.94	83
PCB Mount		Solder	.062 inch End Launch	PE4874	$31.45	$29.88	$28.31	$27.05	84
			Thru Hole with .200 inch x .067 inch Hole Spacing	PE4869	$27.34	$25.97	$24.61	$23.51	85
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188 with .235 inch D Hole	PE4858	$46.60	$44.27	$41.94	$40.08	86
			RG178, RG196 with .235 inch D Hole	PE4861	$41.92	$39.82	$37.73	$36.05	87
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, LMR-195, PE-C195, PE-P195 with .235 inch D Hole	PE4854	$41.92	$39.82	$37.73	$36.05	88

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

Reverse Polarity SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, Bulkhead Mount								
Cable Connectors		Crimp/Solder	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100A-FR, PE-C100, PE-B100 with .235 inch D Hole	PE4859	$32.51	$30.88	$29.26	$27.96	89
			RG178, RG196 with .235 inch D Hole	PE4862	$27.95	$26.55	$25.16	$24.04	90
			RG188-DS, RG316-DS with .235 inch D Hole	PE45189	$29.60	$28.12	$26.64	$25.46	91
			RG196, RG178	PE45004	$20.13	$19.32	$18.72	$18.32	92
			RG55, RG141, RG142, RG223, RG400 with .235 inch D Hole	PE4855	$32.62	$30.99	$29.36	$28.05	93
			RG58 with .235 inch D Hole	PE4857	$26.73	$25.39	$24.06	$22.99	94
		Solder/Solder	PE-SR402AL, PE-SR402FL, RG402 with .235 inch D Hole	PE4864	$39.55	$37.57	$35.60	$34.01	95
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405 with .235 inch D Hole	PE4865	$44.69	$42.46	$40.22	$38.43	96
			RG174, RG316, RG188 with .235 inch D Hole	PE4860	$27.84	$26.45	$25.06	$23.94	97
			RG178, RG196 with .235 inch D Hole	PE4863	$27.47	$26.10	$24.72	$23.62	98
			RG58, RG55, RG141, RG142, RG223, RG400 with .235 inch D Hole	PE4856	$27.89	$26.50	$25.10	$23.99	99
PCB Mount		Solder	Thru Hole with .250 inch Diameter	PE4872	$27.59	$26.21	$24.83	$23.73	1
Terminal			Solder Cup with .235 inch D Hole	PE4868	$27.66	$26.28	$24.89	$23.79	2
			Solder Cup with .235 inch D Hole	PE4871	$27.42	$26.05	$24.68	$23.58	3
	Female, 2 Hole Flange Mount								
Terminal		Solder	Solder Cup with .481 inch Hole Spacing	PE4867	$32.55	$30.92	$29.30	$27.99	4
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .340 inch Hole Spacing	PE4866	$23.17	$22.01	$20.85	$19.93	5
	Female Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4870	$40.63	$38.60	$36.57	$34.94	6
	Female Right Angle, Bulkhead Mount								
PCB Mount		Solder	Thru Hole with .250 inch Diameter	PE4875	$53.91	$51.21	$48.52	$46.36	7

Reverse Thread SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE44184	$15.26	$14.65	$14.19	$13.89	8
			RG178, RG196	PE44185	$27.84	$26.45	$25.06	$23.94	9
			RG188-DS, RG316-DS	PE45165	$24.39	$23.17	$21.95	$20.98	10
			RG55, RG141, RG142, RG223, RG400	PE44182	$29.27	$27.81	$26.34	$25.17	11
			RG58	PE44183	$25.45	$24.18	$22.91	$21.89	12
	Male Right Angle								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188	PE44188	$52.36	$49.74	$47.12	$45.03	13
			RG178, RG196	PE44189	$52.36	$49.74	$47.12	$45.03	14
			RG55, RG141, RG142, RG223, RG400	PE44186	$48.92	$46.47	$44.03	$42.07	15
			RG58	PE44187	$41.37	$39.30	$37.23	$35.58	16
	Female								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188	PE44192	$30.78	$29.24	$27.70	$26.47	17
			RG178, RG196	PE44193	$35.26	$33.50	$31.73	$30.32	18
			RG55, RG141, RG142, RG223, RG400	PE44190	$34.54	$32.81	$31.09	$29.70	19
			RG58	PE44191	$28.44	$27.02	$25.60	$24.46	20

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

Reverse Thread SMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female								
PCB Mount		Solder	.062 inch End Launch	PE44201	$34.54	$32.81	$31.09	$29.70	21
			.062 inch End Launch	PE44202	$34.54	$32.81	$31.09	$29.70	22
			Thru Hole with .200 inch x .067 inch Hole Spacing	PE44198	$34.54	$32.81	$31.09	$29.70	23
	Female, Bulkhead Mount								
Cable Connectors		Crimp/Solder	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100A-FR, PE-C100, PE-B100 with .235 inch D Hole	PE44196	$28.64	$27.21	$25.78	$24.63	24
			RG178, RG196 with .235 inch D Hole	PE44197	$34.83	$33.09	$31.35	$29.95	25
			RG55, RG141, RG142, RG223, RG400 with .235 inch D Hole	PE44194	$32.89	$31.25	$29.60	$28.29	26
			RG58 with .235 inch D Hole	PE44195	$29.50	$28.03	$26.55	$25.37	27
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .340 inch Hole Spacing	PE44200	$38.65	$36.72	$34.79	$33.24	28
	Female Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE44199	$38.65	$36.72	$34.79	$33.24	29

SMA, 2.92mm Torque Wrenches

Type	Bit Hex Size (in.)	Preset Torque (in.-lbs.)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
SMA, 2.92mm	5/16 inch	5 in-lbs	PE5019-19	$223.35	See Web for Volume Pricing	
		8 in-lbs	PE5011-1	$256.76		

SMB Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Clamp/Solder	PE-SR405AL, PE-SR405FL, RG405	PE4356	$19.47	$18.69	$18.11	$17.72	30
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE4200	$19.67	$18.69	$17.70	$16.92	31
			RG178, RG196	PE4250	$24.50	$23.28	$22.05	$21.07	32
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4046	$14.50	$13.78	$13.05	$12.47	33
			RG178, RG196	PE4080	$21.15	$20.09	$19.04	$18.19	34
			RG316-DS, RG188-DS	PE44792	$16.52	$15.69	$14.87	$14.21	35
			RG55, RG142, RG223, RG400	PE4593	$20.05	$19.05	$18.05	$17.24	36
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4523	$21.15	$20.09	$19.04	$18.19	37
		Solder/Solder	RG405, PE-SR405FL, PE-SR405FLJ	PE45119	$10.15	$9.64	$9.14	$8.73	38
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4366	$29.00	$27.55	$26.10	$24.94	39
	Plug, Bulkhead Mount								
Terminal		Solder	Solder Cup with .177 inch D Hole	PE4288	$41.76	$39.67	$37.58	$35.91	40

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

SMB Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug Right Angle								
Cable Connectors		Clamp/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE4358	$21.56	$20.48	$19.40	$18.54	41
			RG174, RG316, RG188	PE4260	$37.81	$35.92	$34.03	$32.52	42
			RG178, RG196	PE4261	$42.79	$40.65	$38.51	$36.80	43
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4052	$11.38	$10.81	$10.24	$9.79	44
			RG178, RG196	PE4159	$23.01	$21.86	$20.71	$19.79	45
			RG188-DS, RG316-DS	PE44818	$17.82	$16.93	$16.04	$15.33	46
			RG55, RG142, RG223, RG400	PE4595	$23.78	$22.59	$21.40	$20.45	47
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4522	$25.56	$24.28	$23.00	$21.98	48
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4245	$24.52	$23.29	$22.07	$21.09	49
	Jack								
Cable Connectors		Clamp/Solder	PE-SR405AL, PE-SR405FL, RG405	PE4360	$19.68	$18.70	$17.71	$16.92	50
			RG178, RG196	PE4269	$29.75	$28.26	$26.78	$25.59	51
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4096	$16.74	$15.90	$15.07	$14.40	52
			RG178, RG196	PE4926	$29.48	$28.01	$26.53	$25.35	53
			RG188-DS, RG316-DS	PE45158	$14.61	$13.88	$13.15	$12.56	54
PCB Mount		Solder	.042 inch End Launch	PE44132	$11.44	$10.98	$10.64	$10.41	55
			.042 inch End Launch	PE44137	$24.07	$22.87	$21.66	$20.70	56
			.062 inch End Launch	PE44135	$22.64	$21.51	$20.38	$19.47	57
			.062 inch End Launch	PE44129	$25.74	$24.45	$23.17	$22.14	58
			Surface Mount	PE44119	$11.56	$10.98	$10.40	$9.94	59
			Thru Hole with .200 inch x .067 inch Hole Spacing	PE4174	$8.76	$8.32	$7.88	$7.53	60
	Jack, Bulkhead Mount								
Cable Connectors		Clamp/Solder	PE-SR405AL, PE-SR405FL, RG405	PE4362	$20.49	$19.47	$18.44	$17.62	61
			RG174, RG316, RG188 with .177 inch D Hole	PE4276	$20.81	$19.77	$18.73	$17.90	62
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4097	$19.64	$18.66	$17.68	$16.89	63
			RG178, RG196	PE4364	$18.64	$17.71	$16.78	$16.03	64
			RG188-DS, RG316-DS	PE45159	$16.12	$15.31	$14.51	$13.86	65
			RG55, RG141, RG142, RG223, RG400 with .177 inch D Hole	PE44048	$38.42	$36.50	$34.58	$33.04	66
			RG58	PE44094	$30.96	$29.41	$27.86	$26.63	67
PCB Mount		Solder	Thru Hole with .177 inch D Hole	PE44123	$24.10	$23.14	$22.41	$21.93	68
Terminal			Solder Cup with .177 inch D Hole	PE4170	$17.14	$16.28	$15.43	$14.74	69
			Solder Cup with .177 inch D Hole	PE4167	$9.17	$8.71	$8.25	$7.89	70
	Jack, 2 Hole Flange Mount								
Terminal		Solder	Solder Cup with .328 inch Hole Spacing	PE44139	$35.02	$33.27	$31.52	$30.12	71
	Jack, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .232 inch Hole Spacing	PE44142	$30.42	$28.90	$27.38	$26.16	72
	Jack Right Angle								
PCB Mount		Solder	Surface Mount	PE44121	$27.16	$25.80	$24.44	$23.36	73
			Thru Hole with .200 inch x .067 inch Hole Spacing	PE4177	$13.96	$13.26	$12.56	$12.01	74

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

SMB Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Jack Right Angle, Bulkhead Mount								
PCB Mount		Solder	Thru Hole with .177 inch D Hole	PE44875	$25.29	$24.03	$22.76	$21.75	75
Terminal			Solder Cup with .177 inch D Hole	PE4284	$31.76	$30.17	$28.58	$27.31	76

SMC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4201	$16.49	$15.67	$14.84	$14.18	77
			RG178, RG196	PE4202	$20.87	$19.83	$18.78	$17.95	78
		Crimp/Solder	PE-P195, PE-C195, RG58, RG141, RG303, .195 inch, LMR-195	PE4558	$24.73	$23.49	$22.26	$21.27	79
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4045	$14.48	$13.76	$13.03	$12.45	80
			RG178, RG196	PE4074	$21.27	$20.21	$19.14	$18.29	81
			RG188-DS, RG316-DS	PE45155	$14.31	$13.59	$12.88	$12.31	82
			RG55, RG142, RG223, RG400	PE45396	$25.17	$23.91	$22.65	$21.65	83
		Solder/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44977	$29.47	$28.00	$26.52	$25.34	84
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4367	$17.73	$16.84	$15.96	$15.25	85
	Plug Right Angle								
Cable Connectors		Clamp/Solder	PE-SR405AL, PE-SR405FL, RG405	PE4359	$47.10	$44.75	$42.39	$40.51	86
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4262	$19.66	$18.68	$17.69	$16.91	87
			RG178, RG196	PE4263	$16.87	$16.03	$15.18	$14.51	88
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4051	$19.34	$18.37	$17.41	$16.63	89
			RG178, RG196	PE4160	$20.12	$19.11	$18.11	$17.30	90
			RG316-DS, RG188-DS	PE44876	$18.00	$17.10	$16.20	$15.48	91
			RG55, RG142, RG223, RG400	PE4596	$23.78	$22.59	$21.40	$20.45	92
			RG58, LMR-195	PE45193	$22.27	$21.16	$20.04	$19.15	93
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4246	$66.18	$63.53	$61.55	$60.22	94
	Jack								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188	PE4270	$36.52	$34.69	$32.87	$31.41	95
		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4094	$20.81	$19.77	$18.73	$17.90	96
			RG178, RG196	PE4927	$39.23	$37.27	$35.31	$33.74	97
			RG188-DS, RG316-DS	PE45156	$18.61	$17.68	$16.75	$16.00	98
PCB Mount		Solder	.042 inch End Launch	PE44138	$18.66	$17.91	$17.35	$16.98	99
			.062 inch End Launch	PE44136	$29.47	$28.00	$26.52	$25.34	1
			.062 inch End Launch	PE44130	$55.94	$53.14	$50.35	$48.11	2
			Surface Mount	PE44120	$20.78	$19.74	$18.70	$17.87	3
			Thru Hole with .200 inch x .067 inch Hole Spacing	PE4175	$11.41	$10.84	$10.27	$9.81	4
	Jack, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG174, RG316, RG188 with .177 inch D Hole	PE4278	$34.83	$33.09	$31.35	$29.95	5
			RG178, RG196 with .177 inch D Hole	PE4279	$34.83	$33.09	$31.35	$29.95	6

Connectors

See Our Website For Current Pricing & Real-Time Stock Availability!

* Fits MIL-C-17 and equivalent cable versions only

SMC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Jack, Bulkhead Mount								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch with .177 inch D Hole	PE4095	$23.12	$21.96	$20.81	$19.88	7
			RG178, RG196	PE4365	$35.10	$33.35	$31.59	$30.19	8
			RG188-DS, RG316-DS with .177 inch D Hole	PE45157	$17.57	$16.69	$15.81	$15.11	9
			RG55, RG141, RG142, RG223, RG400	PE44047	$28.60	$27.17	$25.74	$24.60	10
			RG58	PE44095	$28.06	$26.66	$25.25	$24.13	11
		Solder/Solder	RG405, PE-SR405FL, PE-SR405AL with .177 inch D Hole	PE45210	$42.77	$41.06	$39.78	$38.92	12
PCB Mount		Solder	.062 inch End Launch	PE44848	$33.64	$31.96	$30.28	$28.93	13
			Thru Hole	PE45147	$27.06	$25.71	$24.35	$23.27	14
			Thru Hole with .177 inch D Hole	PE44124	$36.07	$34.27	$32.46	$31.02	15
Terminal			Solder Cup with .177 inch D Hole	PE4107	$16.31	$15.49	$14.68	$14.03	16
			Solder Cup with .177 inch D Hole	PE4171	$15.94	$15.14	$14.35	$13.71	17
	Jack, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .232 inch Hole Spacing	PE44143	$25.46	$24.19	$22.91	$21.90	18
	Jack Right Angle								
PCB Mount		Solder	Surface Mount	PE44122	$9.28	$8.82	$8.35	$7.98	19
			Thru Hole with .200 inch x .067 inch Hole Spacing	PE4178	$17.99	$17.09	$16.19	$15.47	20
	Jack Right Angle, Bulkhead Mount								
Terminal		Solder	Solder Cup with .177 inch D Hole	PE4285	$34.84	$33.10	$31.36	$29.96	21

SMP Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	See Web for Volume Pricing	ROW
	Male						
PCB Mount		Solder	.062 inch End Launch	PE44943	$38.81	See Web for Volume Pricing	22
			.092 inch End Launch	PE44942	$47.33		23
			Edge Launch	PE44955	$35.88		24
			End Launch	PE44482	$30.35		25
			End Launch	PE44880	$15.08		26
			End Launch	PE44879	$15.08		27
			End Launch	PE44777	$15.57		28
			Surface Mount	PE45278TR1500	$30,459.60		29
			Surface Mount	PE45278TR1	$40.02		30
			Surface Mount	PE44944	$58.69		31
			Surface Mount	PE44946	$32.86		32
			Surface Mount	PE44947	$90.83		33
			Surface Mount	PE44952	$50.19		34
			Surface Mount	PE44481	$40.75		35
			Thru Hole	PE44480	$39.19		36
			Thru Hole	PE44958	$54.53		37
			Thru Hole	PE44959	$56.87		38
			Thru Hole	PE44960	$32.98		39
			Thru Hole	PE44957	$48.42		40
			Thru Hole	PE44965	$34.29		41
			Thru Hole	PE44966	$44.65		42
			Thru Hole	PE44967	$35.04		43
			Thru Hole	PE44937	$44.52		44
			Thru Hole	PE44940	$73.52		45
			Thru Hole	PE44910	$37.47		46
			Thru Hole	PE44936	$42.37		47
			Thru Hole	PE44849	$15.57		48
			Thru Hole	PE44840	$11.75		49

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

SMP Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
PCB Mount		Solder	Thru Hole	PE44775	$17.48	$16.61	$15.73	$15.03	50
			Thru Hole	PE44776	$11.75	$11.16	$10.58	$10.11	51
			Thru Hole with .100 inch x .031 inch Hole Spacing	PE44348	$37.35	$35.48	$33.62	$32.12	52
Terminal			Pin	PE44779	$23.41	$22.24	$21.07	$20.13	53
			Pin	PE44780	$23.85	$22.66	$21.47	$20.51	54
	Male, Bulkhead Mount								
Cable Connectors		Solder/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44961	$40.86	$38.82	$36.77	$35.14	55
			RG405, PE-SR405FL, PE-SR405FLJ	PE45126	$36.74	$34.90	$33.07	$31.60	56
			RG405, RG405 Tinned, PE-SR405FL, PE-SR405AL, PE-SR405FLJ, PE-SR405TN with 4.83 mm Diameter	PE44483	$52.21	$49.60	$46.99	$44.90	57
	Male, 2 Hole Flange Mount								
Cable Connectors		Solder/Solder	RG405, PE-SR405FL, PE-SR405FLJ	PE45127	$39.04	$37.09	$35.14	$33.57	58
Shroud		None	None	PE44948	$21.71	$20.62	$19.54	$18.67	59
			None	PE44907	$20.11	$19.10	$18.10	$17.29	60
			None	PE44949	$21.52	$20.44	$19.37	$18.51	61
			None	PE44950	$21.92	$20.82	$19.73	$18.85	62
			None	PE44951	$27.16	$25.80	$24.44	$23.36	63
			None	PE44916	$21.11	$20.27	$19.63	$19.21	64
			None	PE44935	$20.31	$19.50	$18.89	$18.48	65
Terminal		Solder	Pin	PE44938	$49.93	$47.43	$44.94	$42.94	66
	Male, Solder								
Shroud		None	None	PE44932	$21.92	$20.82	$19.73	$18.85	67
Terminal		Solder	Pin	PE44933	$44.54	$42.31	$40.09	$38.30	68
			Pin	PE44945	$53.96	$51.26	$48.56	$46.41	69
			Pin	PE44923	$34.92	$33.17	$31.43	$30.03	70
			Pin	PE44924	$36.89	$35.05	$33.20	$31.73	71
			Pin	PE44928	$38.29	$36.38	$34.46	$32.93	72
			Pin	PE44921	$33.30	$31.64	$29.97	$28.64	73
			Pin	PE44922	$38.66	$36.73	$34.79	$33.25	74
			Pin	PE44925	$32.08	$30.48	$28.87	$27.59	75
			Pin	PE44926	$35.69	$33.91	$32.12	$30.69	76
			Pin	PE44927	$30.86	$29.32	$27.77	$26.54	77
			Pin	PE44930	$30.86	$29.32	$27.77	$26.54	78
			Pin	PE44918	$37.61	$35.73	$33.85	$32.34	79
			Pin	PE44919	$38.66	$36.73	$34.79	$33.25	80
			Pin	PE44920	$29.11	$27.65	$26.20	$25.03	81
	Male, Thread-In								
Shroud		None	None	PE44953	$27.73	$26.34	$24.96	$23.85	82
Terminal		Solder	Pin	PE44963	$44.12	$41.91	$39.71	$37.94	83
			Pin	PE44964	$70.99	$67.44	$63.89	$61.05	84
			Pin	PE44909	$46.04	$43.74	$41.44	$39.59	85
			Pin	PE44912	$35.28	$33.52	$31.75	$30.34	86
			Pin	PE44956	$79.38	$75.41	$71.44	$68.27	87
			Pin	PE44931	$55.83	$53.04	$50.25	$48.01	88
	Male Right Angle								
PCB Mount		Solder	Thru Hole	PE44934	$64.60	$61.37	$58.14	$55.56	89

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

SMP Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female								
Cable Connectors		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE45277	$5.20	$4.99	$4.84	$4.73	90
		Solder/Solder	.086 Microporous	PE44917	$31.93	$30.33	$28.74	$27.46	91
			PE-047SR, PE-SR047AL, PE-SR047FL	PE44785	$27.21	$25.85	$24.49	$23.40	92
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44786	$24.89	$23.65	$22.40	$21.41	93
			RG178, RG196	PE44655	$56.23	$53.42	$50.61	$48.36	94
			RG178, RG196	PE45287	$11.54	$10.96	$10.39	$9.92	95
			RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ	PE45285	$11.30	$10.74	$10.17	$9.72	96
PCB Mount		Solder	Thru Hole	PE44939	$76.46	$72.64	$68.81	$65.76	97
	Female Right Angle								
Cable Connectors		Crimp/Solder	RG178, RG196	PE45290	$11.25	$10.69	$10.13	$9.68	98
			RG316, RG174, LMR-100	PE45128	$16.41	$15.59	$14.77	$14.11	99
		Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE45249	$14.44	$13.72	$13.00	$12.42	1
			RG405, PE-SR405AL, PE-SR405FL, PE-SR405FLJ	PE45248	$11.90	$11.31	$10.71	$10.23	2
			RG405, PE-SR405FL, PE-SR405FLJ	PE44915	$31.40	$29.83	$28.26	$27.00	3
		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44274	$58.27	$55.36	$52.44	$50.11	4
			PE-047SR, PE-SR047FL, PE-SR047AL	PE44911	$36.22	$34.41	$32.60	$31.15	5
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44908	$37.46	$35.59	$33.71	$32.22	6
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44275	$37.49	$35.62	$33.74	$32.24	7
			RG178, RG196	PE44914	$43.18	$41.02	$38.86	$37.13	8
			RG405, PE-SR405FL, PE-SR405FLJ	PE44913	$62.95	$59.80	$56.66	$54.14	9

SSMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE44379	$27.59	$26.21	$24.83	$23.73	10
			RG178, RG196	PE44381	$31.72	$30.13	$28.55	$27.28	11
			RG188-DS, RG316-DS	PE44416	$26.85	$25.51	$24.17	$23.09	12
		Solder (Without Contact)	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405	PE44382	$28.60	$27.17	$25.74	$24.60	13
		Solder/Solder	PE-034SR	PE44440	$32.53	$30.90	$29.28	$27.98	14
			PE-047SR, PE-SR047AL, PE-SR047FL	PE44441	$38.70	$36.77	$34.83	$33.28	15
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405	PE44383	$39.13	$37.17	$35.22	$33.65	16
			RG174, RG316, RG188	PE4184	$27.57	$26.19	$24.81	$23.71	17
			RG178, RG196	PE4199	$30.07	$28.57	$27.06	$25.86	18
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE44430	$29.36	$27.89	$26.42	$25.25	19
	Male, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .232 inch Hole Spacing	PE44432	$29.89	$28.40	$26.90	$25.71	20
	Male Right Angle								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE44378	$30.69	$29.16	$27.62	$26.39	21
			RG178, RG196	PE44380	$62.53	$59.40	$56.28	$53.78	22
			RG188-DS, RG316-DS	PE44418	$38.30	$36.39	$34.47	$32.94	23
		Solder/Solder	PE-034SR	PE44420	$62.21	$59.10	$55.99	$53.50	24
			PE-047SR, PE-SR047AL, PE-SR047FL	PE44421	$65.68	$62.40	$59.11	$56.48	25
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405	PE44384	$45.57	$43.29	$41.01	$39.19	26

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

SSMA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male Right Angle								
Cable Connectors		Solder/Solder	RG174, RG316, RG188	PE44401	$38.93	$36.98	$35.04	$33.48	27
			RG178, RG196	PE44402	$37.50	$36.00	$34.88	$34.13	28
			RG188-DS, RG316-DS	PE44419	$33.28	$31.62	$29.95	$28.62	29
	Female								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE44385	$29.52	$28.04	$26.57	$25.39	30
			RG178, RG196	PE44386	$52.06	$49.46	$46.85	$44.77	31
			RG188-DS, RG316-DS	PE44422	$30.85	$29.31	$27.77	$26.53	32
		Solder/Solder	PE-034SR	PE44424	$38.23	$36.32	$34.41	$32.88	33
			PE-047SR, PE-SR047AL, PE-SR047FL	PE44425	$36.45	$34.63	$32.81	$31.35	34
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405	PE44387	$32.65	$31.02	$29.39	$28.08	35
			RG174, RG316, RG188	PE44403	$29.17	$27.71	$26.25	$25.09	36
			RG178, RG196	PE44404	$32.42	$30.80	$29.18	$27.88	37
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE44391	$37.76	$35.87	$33.98	$32.47	38
	Female, Bulkhead Mount								
Cable Connectors		Crimp/Solder	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100A-FR, PE-C100, PE-B100 with .177 inch D Hole	PE44388	$48.56	$46.13	$43.70	$41.76	39
			RG178, RG196 with .177 inch D Hole	PE44389	$43.49	$41.32	$39.14	$37.40	40
			RG188-DS, RG316-DS with .177 inch D Hole	PE44426	$33.11	$31.45	$29.80	$28.47	41
		Solder/Solder	PE-034SR with .177 inch D Hole	PE44428	$50.61	$48.08	$45.55	$43.52	42
			PE-047SR, PE-SR047AL, PE-SR047FL with .177 inch D Hole	PE44429	$54.72	$51.98	$49.25	$47.06	43
			PE-SR405AL, PE-SR405FL, RG405 with .177 inch D Hole	PE44390	$38.65	$36.72	$34.79	$33.24	44
			RG174, RG316, RG188 with .177 inch D Hole	PE44405	$28.03	$26.63	$25.23	$24.11	45
			RG178, RG196 with .177 inch D Hole	PE44406	$30.85	$29.31	$27.77	$26.53	46
			RG188-DS, RG316-DS with .177 inch D Hole	PE44427	$27.47	$26.10	$24.72	$23.62	47
PCB Mount		Solder	.042 inch End Launch	PE45405	$30.25	$28.74	$27.23	$26.02	48
			.062 inch End Launch	PE45406	$30.25	$28.74	$27.23	$26.02	49
Terminal			Solder Cup with .177 inch D Hole	PE44393	$34.98	$33.23	$31.48	$30.08	50
			Turret with .177 inch D Hole	PE44392	$41.66	$39.58	$37.49	$35.83	51
	Female, 2 Hole Flange Mount								
Cable Connectors		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL with .328 inch Hole Spacing	PE44436	$49.10	$46.65	$44.19	$42.23	52
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, RG405 with .328 inch Hole Spacing	PE44437	$26.62	$25.29	$23.96	$22.89	53
Terminal		Solder	Pin with .328 inch Hole Spacing	PE44433	$53.61	$50.93	$48.25	$46.10	54
			Solder Cup with .328 inch Hole Spacing	PE44395	$53.64	$50.96	$48.28	$46.13	55
	Female, 4 Hole Flange Mount								
Terminal		Solder	Pin with .232 inch Hole Spacing	PE44434	$48.73	$46.29	$43.86	$41.91	56
			Solder Cup with .232 inch Hole Spacing	PE44394	$41.38	$39.31	$37.24	$35.59	57
Cable Connectors		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL with .232 inch Hole Spacing	PE44438	$50.07	$47.57	$45.06	$43.06	58
			PE-SR405AL, PE-SR405FL, RG405 with .232 inch Hole Spacing	PE44439	$41.92	$39.82	$37.73	$36.05	59
	Female Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE44435	$67.86	$64.47	$61.07	$58.36	60

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

SSMB Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4017	$38.59	$36.66	$34.73	$33.19	61
			RG188-DS, RG316-DS	PE45153	$31.34	$29.77	$28.21	$26.95	62
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG174, RG179, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE4334	$59.29	$56.33	$53.36	$50.99	63
			RG178, RG196	PE45195	$23.08	$21.93	$20.77	$19.85	64
			RG188-DS, RG316-DS	PE45162	$30.85	$29.62	$28.69	$28.07	65
	Jack								
Cable Connectors		Crimp/Solder	RG178, RG196	PE4019	$31.89	$30.30	$28.70	$27.43	66
PCB Mount		Solder	Thru Hole with .100 inch x .031 inch Hole Spacing	PE4340	$16.58	$15.75	$14.92	$14.26	67
	Jack, Bulkhead Mount								
Cable Connectors		Crimp/Solder	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100A-FR, PE-C100, PE-B100 with .126 inch D Hole	PE4336	$42.89	$40.75	$38.60	$36.89	68
			RG178, RG196 with .126 inch D Hole	PE4337	$37.62	$35.74	$33.86	$32.35	69
			RG316-DS, RG188-DS with .126 inch D Hole	PE44842	$33.20	$31.54	$29.88	$28.55	70
Terminal		Solder	Turret with .126 inch D Hole	PE4338	$28.14	$26.73	$25.33	$24.20	71
			Turret with .126 inch D Hole	PE4339	$29.18	$27.72	$26.26	$25.09	72
	Jack, 4 Hole Flange Mount								
Terminal		Solder	Tab with .164 inch x .067 inch Hole Spacing	PE44455	$28.36	$26.94	$25.52	$24.39	73
	Jack Right Angle								
PCB Mount		Solder	Thru Hole with .100 inch x .031 inch Hole Spacing	PE4341	$28.80	$27.36	$25.92	$24.77	74

SSMC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Clamp/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE45366	$28.05	$26.65	$25.25	$24.12	75
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE45365	$26.81	$25.47	$24.13	$23.06	76
		Crimp/Solder	LMR-100A, RG188, RG174, PE-C100-LSZH, PE-B100, LMR-100A-FR, RG316	PE45491	$27.57	$26.19	$24.81	$23.71	77
			RG178, RG196	PE45490	$29.30	$27.84	$26.37	$25.20	78
			RG188-DS, RG316-DS	PE45492	$28.63	$26.63	$24.62	$22.90	79
			RG316, RG174, RG188	PE45209	$16.94	$16.09	$15.25	$14.57	80
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG178, RG196	PE45496	$20.86	$19.82	$18.77	$17.94	81
			RG316, RG188, RG174, PE-C100-LSZH, PE-B100, LMR-100A-FR, LMR-100A	PE45497	$23.79	$22.60	$21.41	$20.46	82
			RG316-DS, RG188-DS	PE45498	$23.00	$21.39	$19.78	$18.40	83
		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE45385	$26.93	$25.58	$24.24	$23.16	84
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE45384	$25.72	$24.43	$23.15	$22.12	85
PCB Mount		Solder	Thru Hole	PE45379	$32.56	$30.93	$29.30	$28.00	86

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

SSMC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	PRICE See Web for Volume Pricing			ROW
	Jack								
PCB Mount		Solder	Surface Mount	PE45376	$22.85				87
	Jack, Bulkhead Mount								
Cable Connectors		Clamp/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE45371	$26.77	See Web for Volume Pricing			88
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE45370	$19.32				89
		Crimp/Solder	RG-178, RG-196	PE45493	$25.73				90
			RG316, RG188	PE45494	$25.43				91
Terminal		Solder	Turret	PE45375	$21.02				92
			Turret	PE45390	$19.41				93
	Jack, 2 Hole Flange Mount								
Terminal		Solder	Solder Cup	PE45380	$116.78				94
	Jack, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup	PE45391	$69.16				95
	Jack Right Angle								
PCB Mount		Solder	Surface Mount	PE45377	$30.76				96
	Jack Right Angle, Bulkhead Mount								
Cable Connectors		Crimp/Solder	PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE45387	$35.82	See Web for Volume Pricing			97
			RG178, RG196	PE45499	$23.05				98
		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE45388	$39.84				99
PCB Mount		Solder	Turret	PE45389	$45.59				1
Terminal			Turret	PE45378	$42.30				2

TNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	PRICE 25-49	PRICE 50-99	PRICE 100 +	ROW
	Sexless								
Cable Connectors		Accessories	RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4022	$2.38	$2.26	$2.14	$2.05	3
	Male								
Cable Connectors		Clamp/Solder	PE-C200	PE44061	$18.23	$17.32	$16.41	$15.68	4
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE4449	$22.43	$21.53	$20.86	$20.41	5
			PE-P142LL	PE44815	$71.38	$67.81	$64.24	$61.39	6
			PE-P160LL	PE45443	$80.44	$76.42	$72.40	$69.18	7
			PE-P300LL	PE44810	$108.89	$103.45	$98.00	$93.65	8

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

TNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	PRICE See Web for Volume Pricing	ROW
	Male						
Cable Connectors		Clamp/Solder	PE-SR402AL, PE-SR402FL, RG402	PE4143	$25.07	See Web for Volume Pricing	9
			PE-SR405AL, PE-SR405FL, RG405	PE4142	$22.79		10
			RG174, RG316, RG188	PE4303	$17.36		11
			RG178, RG196	PE4448	$21.89		12
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG215, RG216*	PE4088	$22.21		13
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4067	$28.23		14
			RG59*, RG62*, RG71	PE4154	$18.29		15
			RG8X, PE-C240, .240 inch, B7808A, LMR-240	PE45437	$23.74		16
		Crimp/Crimp	PE-C200, LMR-200	PE44804	$11.33		17
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4302	$23.32		18
			RG188-DS, RG316-DS	PE45161	$22.80		19
			RG55, RG142, RG223, RG400	PE4047	$14.70		20
		Crimp/ Non-Solder Contact	LMR-200, PE-C200	EZ-200-TM-X	$20.75		21
			LMR-240, PE-C240	EZ-240-TM-X	$14.78		22
			LMR-400, PE-C400, PE-B400, PE-B405	EZ-400-TM-X	$13.55		23
			LMR-600, PE-C600	EZ-600-TM-X	$20.33		24
		Crimp/Solder	LMR-100A-PVC, PE-C100, RG174, RG188, RG316	SC-100-TM-D	$18.86		25
			LMR-195, PE-C195	TC-195-TM-X	$15.25		26
			LMR-240, PE-C240	TC-240-TM-X	$12.32		27
			LMR-400, PE-C400	TC-400-TM-X	$12.01		28
			PE-C200	PE44062	$20.05		29
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44634	$15.36		30
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44293	$37.49		31
			RG122, RG58 Plenum, RG58-P	PE45065	$7.31		32
			RG213, RG8	PE4446	$21.49		33
			RG214, RG9, RG225, RG393	PE4447	$31.51		34
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4156	$8.87		35
			RG59*, RG62*, RG71	PE4071	$14.55		36
		Solder/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE4975	$31.41		37
			PE-SR401AL, PE-SR401FL, RG401	PE4909	$73.13		38
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44709	$16.94		39
			PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402 with .480 inch D Hole	PE4648	$34.32		40
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44708	$16.94		41
			PE-SR405AL, PE-SR405FL, RG405	PE4649	$31.61		42
	Male, 4 Hole Flange Mount						
Terminal		Solder	Pin with .531 inch Hole Spacing	PE44654	$81.51		43
			Solder Cup with .531 inch Hole Spacing	PE4470	$25.60		44
	Male Right Angle						
Cable Connectors		Clamp/Solder	PE-P142LL	PE44812	$158.00	See Web for Volume Pricing	45
			PE-P160LL	PE45445	$142.68		46
			RG174, RG316, RG188	PE4454	$23.20		47
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4146	$39.94		48
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4054	$29.78		49
			RG59*, RG62*	PE4452	$51.79		50
		Crimp/Crimp	RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4451	$31.51		51
		Crimp/Solder	LMR-400, PE-C400	TC-400-TM-RA-D	$25.87		52
			PE-C200, LMR-200	PE44846	$21.86		53
			PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44635	$27.24		54
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE4455	$29.73		55
			RG188-DS, RG316-DS	PE45174	$25.94		56
			RG55, RG141, RG142, RG223, RG400	PE4450	$19.49		57

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

TNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1 Pc.	PRICE See Web for Volume Pricing			ROW
	Male Right Angle								
Cable Connectors		Solder/Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44711	$17.97				58
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44710	$17.96				59
	Female								
Cable Connectors		Clamp/Solder	PE-SR402AL, PE-SR402FL, RG402	PE4145	$25.06		See Web for Volume Pricing		60
			PE-SR405AL, PE-SR405FL, RG405	PE4144	$25.06				61
			RG174, RG316, RG188	PE4461	$17.86				62
			RG178, RG196	PE4463	$20.05				63
			RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE4155	$42.65				64
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4068	$15.95				65
			RG59*, RG62*, RG71	PE4460	$17.69				66
		Crimp/Solder	PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44636	$21.31				67
			RG174, RG316, RG188, PE-B100, PE-C100, .100 inch, LMR-100	PE4462	$23.18				68
			RG316, RG174, LMR-100	PE45143	$11.44				69
			RG55, RG142, RG223, RG400	PE4457	$17.01				70
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4458	$18.09				71
			RG59*, RG62*, RG71	PE4459	$19.47				72
		Solder	LMR-400, LMR-400-DB, LMR-400-UF, PE-B400, PE-B405, PE-C400	PE45639	$6.97				73
		Solder/Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44713	$16.94				74
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44712	$14.53				75
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	PE-047SR, PE-SR047AL, PE-SR047FL	PE44897	$36.68		See Web for Volume Pricing		76
			PE-P142LL	PE44811	$106.68				77
			PE-P160LL	PE45444	$109.39				78
			PE-SR402AL, PE-SR402FL, RG402 with .480 inch D Hole	PE4150	$29.17				79
			PE-SR405AL, PE-SR405FL, RG405 with .480 inch D Hole	PE4149	$29.17				80
			RG174, RG316, RG188 with .480 inch D Hole	PE4304	$24.61				81
			RG178, RG196 with .480 inch D Hole	PE4467	$23.20				82
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, PE-C195, PE-P195 with .480 inch D Hole	PE4152	$20.79				83
			RG59*, RG62*, RG71 with .480 inch D Hole	PE4464	$35.16				84
		Crimp/Solder	RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE44899	$65.62				85
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE44900	$66.88				86
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch with .480 inch D Hole	PE4466	$28.02				87
			RG188-DS, RG316-DS with .480 inch D Hole	PE45177	$25.44				88
			RG55, RG142, RG223, RG400 with .480 inch D Hole	PE4153	$21.88				89
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch with .480 inch D Hole	PE4151	$23.72				90
			RG59*, RG62* with .480 inch D Hole	PE4465	$27.29				91
		Solder	RG178, RG196	PE45132	$25.41				92
		Solder/Solder	PE-SR402AL, PE-SR402FL, PE-SR402FLJ, PE-SR402TN, RG402	PE44715	$20.14				93
			PE-SR402AL, PE-SR402FL, RG402 with .480 inch D Hole	PE4148	$77.94				94
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44714	$20.71				95
			PE-SR405AL, PE-SR405FL, PE-SR405FLJ, PE-SR405TN, RG405	PE44898	$54.50				96
PCB Mount		Solder	Edge Mount	PE44894	$74.48				97

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

TNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, Bulkhead Mount								
Terminal		Solder	Eyelet with .350 inch D Hole	PE4305	$37.45	$35.58	$33.71	$32.21	98
			Eyelet with .480 inch D Hole	PE4469	$48.72	$46.28	$43.85	$41.90	99
			None	PE45130	$14.61	$13.88	$13.15	$12.56	1
			Solder Cup with .350 inch D Hole	PE4065	$17.14	$16.28	$15.43	$14.74	2
			Solder Cup with .350 inch D Hole	PE4306	$14.96	$14.21	$13.46	$12.87	3
			Solder Cup with .410 inch D Hole	PE4063	$27.34	$25.97	$24.61	$23.51	4
			Solder Cup with .480 inch D Hole	PE4468	$21.30	$20.24	$19.17	$18.32	5
	Female, 4 Hole Flange Mount								
Cable Connectors		Clamp/Solder	RG316-DS, RG188-DS	PE44901	$39.62	$37.64	$35.66	$34.07	6
Terminal		Solder	Solder Cup with .500 inch Hole Spacing	PE4064SP	$24.88	$23.64	$22.39	$21.40	7
			Solder Cup with .500 inch Threaded Hole Spacing	PE4064	$16.87	$16.03	$15.18	$14.51	8
	Female Right Angle								
PCB Mount		Solder/Solder	Thru Hole with .380 inch x .083 inch Hole Spacing	PE44659	$19.44	$18.47	$17.50	$16.72	9
	Female Right Angle, Bulkhead Mount								
Cable Connectors		Crimp/Solder	PE-C200, LMR-200 with .480 inch D Hole	PE44847	$24.97	$23.72	$22.47	$21.47	10
PCB Mount		Solder	Surface Mount	PE44892	$76.22	$72.41	$68.60	$65.55	11
Terminal			Solder Cup with .361 inch D Hole	PE4471	$35.78	$33.99	$32.20	$30.77	12

Reverse Polarity TNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	PE-B400, PE-B405	PE4674	$24.99	$23.74	$22.49	$21.49	13
			PE-SR402AL, PE-SR402FL, RG402	PE4670	$26.04	$24.74	$23.44	$22.39	14
			PE-SR405AL, PE-SR405FL, RG405	PE4672	$26.81	$25.47	$24.13	$23.06	15
			RG174, RG316, RG188	PE4667	$24.73	$23.49	$22.26	$21.27	16
			RG178, RG196	PE4669	$22.11	$21.00	$19.90	$19.01	17
			RG213, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4659	$27.30	$25.94	$24.57	$23.48	18
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4662	$16.83	$15.99	$15.15	$14.47	19
			RG59*, RG62*, RG71	PE4665	$16.95	$16.10	$15.26	$14.58	20
		Crimp/Crimp	LMR-200, PE-C200	PE45283	$22.07	$20.97	$19.86	$18.98	21
		Crimp/Solder	PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44670	$14.36	$13.64	$12.92	$12.35	22
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44672	$27.78	$26.39	$25.00	$23.89	23
			RG174, RG316, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4668	$27.52	$26.42	$25.59	$25.04	24
			RG188-DS, RG316-DS	PE45180	$25.32	$24.31	$23.55	$23.04	25
			RG213, RG8	PE4660	$24.86	$23.62	$22.37	$21.38	26
			RG214, RG9, RG225, RG393	PE4661	$28.26	$26.85	$25.43	$24.30	27
			RG55, RG141, RG142, RG223, RG400	PE4663	$17.25	$16.39	$15.53	$14.84	28
			RG58	PE4664	$14.79	$14.05	$13.31	$12.72	29
			RG59*, RG62*, RG71	PE4666	$17.35	$16.48	$15.62	$14.92	30
		Solder/Solder	PE-SR402AL, PE-SR402FL, RG402	PE4671	$35.99	$34.19	$32.39	$30.95	31
			PE-SR405AL, PE-SR405FL, RG405	PE4673	$53.36	$50.69	$48.02	$45.89	32

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

Reverse Polarity TNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .531 inch Hole Spacing	PE4708	$28.14	$26.73	$25.33	$24.20	33
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG178, RG196	PE4682	$29.50	$28.03	$26.55	$25.37	34
			RG316, RG174, RG188	PE4680	$27.37	$26.00	$24.63	$23.54	35
			RG58, RG55, RG141, RG142, RG223, RG400	PE4676	$38.23	$36.32	$34.41	$32.88	36
			RG59*, RG62*	PE4679	$32.99	$31.34	$29.69	$28.37	37
		Crimp/Solder	RG316, RG174, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4681	$32.18	$30.57	$28.96	$27.67	38
			RG55, RG141, RG142, RG223, RG400	PE4677	$27.30	$25.94	$24.57	$23.48	39
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4678	$29.78	$28.29	$26.80	$25.61	40
	Female								
Cable Connectors		Clamp/Solder	PE-SR402AL, PE-SR402FL, RG402	PE4692	$24.73	$23.49	$22.26	$21.27	41
			PE-SR405AL, PE-SR405FL, RG405	PE4693	$25.55	$24.27	$23.00	$21.97	42
			RG178, RG196	PE4691	$19.88	$18.89	$17.89	$17.10	43
			RG213, RG8, RG215, RG225, RG214, RG393	PE4683	$48.88	$46.44	$43.99	$42.04	44
			RG316, RG174, RG188	PE4689	$19.16	$18.20	$17.24	$16.48	45
			RG58, RG55, RG141, RG142, RG223, RG400	PE4684	$21.76	$20.67	$19.58	$18.71	46
			RG59*, RG62*	PE4688	$25.82	$24.53	$23.24	$22.21	47
		Crimp/ Non-Solder Contact	LMR-200, PE-C200	EZ-200-TF-RP	$18.21	$18.21	$18.21	$18.21	48
		Crimp/Solder	PE-C240, RG8X, .240 inch, LMR-240, LMR-240-DB, LMR-240-UF, B7808A	PE44671	$21.71	$20.62	$19.54	$18.67	49
			PE-C400, PE-B400, PE-B405, LMR-400, LMR-400-DB, LMR-400-UF, .400 inch	PE44673	$19.34	$18.37	$17.41	$16.63	50
			RG316, RG174, RG188, LMR-100, PE-B100, PE-C100, .100 inch	PE4690	$25.69	$24.41	$23.12	$22.09	51
			RG55, RG142, RG223, RG400	PE4685	$17.82	$16.93	$16.04	$15.33	52
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4686	$20.12	$19.11	$18.11	$17.30	53
			RG59*, RG62*	PE4687	$21.71	$20.62	$19.54	$18.67	54
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	PE-SR402AL, PE-SR402FL, RG402 with .480 inch D Hole	PE4702	$29.76	$28.27	$26.78	$25.59	55
			PE-SR405AL, PE-SR405FL, RG405 with .480 inch D Hole	PE4703	$29.50	$28.03	$26.55	$25.37	56
			RG178, RG196 with .480 inch D Hole	PE4701	$26.46	$25.14	$23.81	$22.76	57
			RG316, RG174, RG188 with .480 inch D Hole	PE4699	$27.37	$26.00	$24.63	$23.54	58
			RG58, RG142, RG223, RG400, RG141, RG303, RG55, PE-C195, PE-P195 with .480 inch D Hole	PE4694	$25.50	$24.23	$22.95	$21.93	59
		Crimp/Solder	.100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100A-FR, PE-C100, PE-B100 with .480 inch D Hole	PE4700	$30.64	$29.11	$27.58	$26.35	60
			.195 inch, RG58, RG141, RG303, LMR-195, LMR-195-FR, PE-C195, PE-P195 with .480 inch D Hole	PE4696	$30.25	$28.74	$27.23	$26.02	61
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE44902	$55.73	$52.94	$50.16	$47.93	62
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE44903	$63.69	$60.51	$57.32	$54.77	63
			RG188-DS, RG316-DS with .480 inch D Hole	PE45181	$26.78	$25.44	$24.10	$23.03	64
			RG55, RG141, RG142, RG223, RG400 with .480 inch D Hole	PE4695	$23.35	$22.18	$21.02	$20.08	65
Terminal		Solder	Solder Cup with .350 inch D Hole	PE4706	$22.60	$21.47	$20.34	$19.44	66
			Solder Cup with .410 inch D Hole	PE4704	$22.60	$21.47	$20.34	$19.44	67
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .500 inch Threaded Hole Spacing	PE4705	$28.57	$27.14	$25.71	$24.57	68

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

TNC Torque Wrenches

Type	Bit Hex Size (in.)	Preset Torque (in.-lbs.)	Model No	1-9	10-24	25-49	50+	ROW
TNC	5/8 inch	14 in-lbs	PE5011-4	$360.10	$342.10	$324.09	$309.69	
	9/16 inch	13 in-lbs	PE5011-8	$339.73	$322.74	$305.76	$292.17	
	5/8 inch	12 in-lbs	PE5019-10	$240.14	$228.13	$216.13	$206.52	

UHF Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Sexless								
Cable Connectors		Accessories	RG59*, RG62*, RG71	PE4021	$2.19	$2.08	$1.97	$1.88	69
	Male								
Cable Connectors		Clamp/Solder	RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG215, RG216*	PE44050	$14.77	$14.03	$13.29	$12.70	70
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE44052	$13.86	$13.17	$12.47	$11.92	71
		Crimp/Solder	PE-B400, PE-B405, PE-C400, LMR-400, .400 inch	PE44054	$15.38	$14.61	$13.84	$13.23	72
			RG213, RG215, RG8	PE4295	$18.83	$17.89	$16.95	$16.19	73
			RG214, RG9, RG225, RG393	PE44051	$16.63	$15.80	$14.97	$14.30	74
			RG55, RG141, RG142, RG223, RG400	PE44053	$11.27	$10.71	$10.14	$9.69	75
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE4069	$12.28	$11.67	$11.05	$10.56	76
			RG59*, RG62*, RG71	PE4073	$10.04	$9.54	$9.04	$8.63	77
		Solder	RG213, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE4020	$17.71	$16.82	$15.94	$15.23	78
			RG59*, RG62*, RG71	PE44828	$16.04	$15.24	$14.44	$13.79	79
	Female								
Cable Connectors		Clamp/Solder	RG213, RG214, RG8, RG9, RG11*, RG225, RG393, RG144*, RG216*, RG215	PE44055	$18.46	$17.54	$16.61	$15.88	80
			RG58, RG55, RG141, RG142, RG223, RG400, RG303, PE-C195, PE-P195, LMR-195	PE44056	$19.47	$18.50	$17.52	$16.74	81
		Crimp/Solder	RG55, RG141, RG142, RG223, RG400	PE44057	$15.12	$14.36	$13.61	$13.00	82
			RG58, RG303, RG141, PE-C195, PE-P195, LMR-195, .195 inch	PE44058	$19.47	$18.50	$17.52	$16.74	83
	Female, Bulkhead Mount								
Terminal		Solder	Solder Cup with .575 inch D Hole	PE44059	$14.69	$13.96	$13.22	$12.63	84
			Solder Cup with .575 inch D Hole	PE44060	$12.64	$12.01	$11.38	$10.87	85
	Female, 4 Hole Flange Mount								
Terminal		Field Replaceable	Slotted Contact	PE44719	$59.56	$56.58	$53.60	$51.22	86
		Solder	Solder Cup with .718 inch Hole Spacing	PE45478	$10.69	$9.94	$9.19	$8.55	87

UMCX Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Jack								
PCB Mount		Solder	Surface Mount	PE44594	$2.06	$1.96	$1.85	$1.77	88

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

75 Ohm 1.0/2.3 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Crimp	BELDEN 1855A	PE45228	$12.49	$11.87	$11.24	$10.74	89
			BELDEN 735A1	PE45227	$12.86	$12.22	$11.57	$11.06	90
			RG179-DS	PE45233	$12.86	$12.22	$11.57	$11.06	91
			RG59*	PE45234	$12.86	$12.22	$11.57	$11.06	92
			RG6-CATV	PE45235	$19.11	$18.15	$17.20	$16.43	93
	Jack, Bulkhead Mount								
PCB Mount		Solder	End Launch	PE45232	$21.25	$20.19	$19.13	$18.28	94
			Thru Hole	PE45231	$19.07	$18.12	$17.16	$16.40	95
			Thru Hole	PE45229	$17.39	$16.52	$15.65	$14.96	96
	Jack Right Angle, Bulkhead Mount								
PCB Mount		Solder	Thru Hole	PE45230	$16.42	$15.60	$14.78	$14.12	97
			Thru Hole	PE45237	$19.41	$18.44	$17.47	$16.69	98

75 Ohm 1.6/5.6 Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG179, RG187	PE44262	$19.47	$18.50	$17.52	$16.74	99
			RG59*, RG62*, RG71	PE44263	$18.46	$17.54	$16.61	$15.88	1
	Plug Right Angle								
Cable Connectors		Clamp/Solder	RG179, RG187	PE44264	$19.73	$18.74	$17.76	$16.97	2
	Jack, Bulkhead Mount								
PCB Mount		Solder	Thru Hole with .362 inch Diameter	PE44270	$17.14	$16.28	$15.43	$14.74	3
	Jack Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .052 inch Hole Spacing	PE44271	$19.73	$18.74	$17.76	$16.97	4
	Jack Right Angle, Bulkhead Mount								
Cable Connectors		Crimp/Solder	RG179, RG187 with .362 inch DD Hole	PE44268	$19.73	$18.74	$17.76	$16.97	5

75 Ohm BNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	RG11*, RG144*, RG216*	PE4599	$38.60	$36.67	$34.74	$33.20	6
			RG179, RG187	PE4603	$17.48	$16.61	$15.73	$15.03	7
			RG59*, RG62*, RG71	PE4601	$18.93	$17.98	$17.04	$16.28	8
		Compression	Mini 59, PE-B159	PE44578	$18.09	$17.19	$16.28	$15.56	9
			PE-B159, 1855A, Mini 59	PE44577	$15.76	$14.97	$14.18	$13.55	10
		Crimp/Crimp	RG59*, RG62*, RG71	PE4602	$12.49	$11.87	$11.24	$10.74	11
		Crimp/Solder	1505A	PE44631	$6.62	$6.29	$5.96	$5.69	12
			1505A	PE44626	$12.96	$12.31	$11.66	$11.15	13
			1694A	PE44627	$6.24	$5.93	$5.62	$5.37	14

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

75 Ohm BNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Crimp/Solder	1694A	PE44632	$17.44	$16.57	$15.70	$15.00	15
			735A	PE44686	$30.52	$28.99	$27.47	$26.25	16
			7731A	PE44628	$11.10	$10.55	$9.99	$9.55	17
			Belden 150A	PE45117	$10.49	$9.97	$9.44	$9.02	18
			Belden 1694A	PE45116	$13.65	$12.97	$12.29	$11.74	19
			PE-B150, RG180, RG195	PE4633	$16.55	$15.72	$14.90	$14.23	20
			PE-B159, 1855A, Mini 59	PE44625	$13.65	$12.97	$12.29	$11.74	21
			PE-B159, 1855A, Mini 59	PE44584	$17.25	$16.39	$15.53	$14.84	22
			PE-B305	PE4634	$17.70	$16.82	$15.93	$15.22	23
			RG11*, RG216*, RG144*	PE4600	$24.17	$22.96	$21.75	$20.79	24
			RG179, RG187	PE4604	$15.06	$14.31	$13.55	$12.95	25
			RG6	PE4598	$8.03	$7.63	$7.23	$6.91	26
	Male, Bulkhead Mount								
Terminal		Solder	Solder Cup with .350 inch D Hole	PE4627	$24.71	$23.47	$22.24	$21.25	27
	Male, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .531 inch Hole Spacing	PE4625	$22.99	$21.84	$20.69	$19.77	28
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG179, RG187	PE4609	$56.39	$53.57	$50.75	$48.50	29
			RG59*, RG62*, RG71	PE4607	$50.45	$47.93	$45.41	$43.39	30
			RG6	PE4605	$40.32	$38.30	$36.29	$34.68	31
		Crimp/Solder	RG179, RG187	PE4610	$27.40	$26.03	$24.66	$23.56	32
			RG59*, RG62*, RG71	PE4608	$36.71	$34.87	$33.04	$31.57	33
	Female								
Cable Connectors		Clamp/Solder	RG179, RG187	PE4615	$30.76	$29.53	$28.61	$27.99	34
			RG59*	PE4613	$23.60	$22.42	$21.24	$20.30	35
			RG6	PE4611	$46.71	$44.37	$42.04	$40.17	36
		Crimp/Solder	735A	PE44688	$29.38	$27.91	$26.44	$25.27	37
			RG179, RG187	PE4616	$21.18	$20.12	$19.06	$18.21	38
PCB Mount		Solder	End Launch	PE44619	$11.89	$11.30	$10.70	$10.23	39
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG179, RG187 with .480 inch D Hole	PE4639	$37.50	$36.00	$34.88	$34.13	40
			RG59*, RG62*, RG71 with .480 inch D Hole	PE4637	$39.31	$37.34	$35.38	$33.81	41
		Crimp/Solder	735A with .480 inch D Hole	PE44687	$31.41	$29.84	$28.27	$27.01	42
			PE-B150, RG180, RG195 with .480 inch D Hole	PE4641	$30.52	$28.99	$27.47	$26.25	43
			PE-B159, 1855A, Mini 59 with .480 inch D Hole	PE44587	$25.45	$24.18	$22.91	$21.89	44
			PE-B305 with .480 inch D Hole	PE4642	$34.95	$33.20	$31.46	$30.06	45
			RG179, RG187 with .480 inch D Hole	PE4640	$25.73	$24.44	$23.16	$22.13	46
			RG59*, RG62*, RG71 with .480 inch D Hole	PE4638	$32.74	$31.10	$29.47	$28.16	47
PCB Mount		Solder	End Launch with .500 inch Diameter	PE44620	$19.29	$18.33	$17.36	$16.59	48
Terminal			Solder Cup with .350 inch D Hole	PE4626	$14.81	$14.07	$13.33	$12.74	49
			Solder Cup with .350 inch D Hole	PE4620	$16.58	$15.75	$14.92	$14.26	50
			Solder Cup with .410 inch D Hole	PE4619	$12.19	$11.58	$10.97	$10.48	51
			Turret with .350 inch D Hole	PE4624	$40.29	$38.28	$36.26	$34.65	52
			Turret with .480 inch D Hole	PE4621	$49.59	$47.11	$44.63	$42.65	53
	Female, 4 Hole Flange Mount								
Cable Connectors		Clamp/Solder	RG179, RG187 with .500 inch Threaded Hole Spacing	PE44652	$38.55	$36.62	$34.70	$33.15	54
			RG59*, RG62*, RG71 with .500 inch Threaded Hole Spacing	PE4623	$40.22	$38.21	$36.20	$34.59	55

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

75 Ohm BNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .500 inch Threaded Hole Spacing	PE4617	$18.04	$17.14	$16.24	$15.51	56
			Solder Cup with .500 inch Hole Spacing	PE4630	$22.60	$21.47	$20.34	$19.44	57
			Solder Cup with .718 inch Hole Spacing	PE4631	$30.38	$28.86	$27.34	$26.13	58
			Turret with .531 inch Hole Spacing	PE4618	$49.00	$46.55	$44.10	$42.14	59
	Female Right Angle, Bulkhead Mount								
Terminal		Solder	Solder Cup with .361 inch D Hole	PE4622	$60.53	$57.50	$54.48	$52.06	60
	Female Right Angle, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .531 inch Hole Spacing	PE4628	$28.66	$27.23	$25.79	$24.65	61

75 Ohm F Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Compression	PE-B159, 1855A, Mini 59	PE44572	$7.35	$6.98	$6.62	$6.32	62
			PE-B159, 1855A, Mini 59	PE44573	$6.39	$6.07	$5.75	$5.50	63
		Crimp/Crimp	RG59*, RG62*, RG71	PE44317	$6.21	$5.90	$5.59	$5.34	64
			RG6	PE44312	$2.64	$2.51	$2.38	$2.27	65
		Crimp/ Non-Solder Contact	LMR-400-75	EZ-400-FM-75	$29.38	$29.38	$29.38	$29.38	66
		Crimp/Solder	PE-B159, 1855A, Mini 59	PE44582	$6.59	$6.26	$5.93	$5.67	67
			RG11*, RG216*, RG144*	PE44315	$7.65	$7.27	$6.89	$6.58	68
			RG179, RG187	PE45520	$4.53	$4.30	$4.08	$3.90	69
			RG59*, RG62*, RG71	PE44316	$1.60	$1.52	$1.44	$1.38	70
			RG6-CATV	PE44313	$6.24	$5.93	$5.62	$5.37	71
			RG6-CATV	PE44452	$3.44	$3.27	$3.10	$2.96	72
		Twist	RG59*, RG62*, RG71	PE44318	$1.85	$1.76	$1.67	$1.59	73
			RG6	PE44314	$2.90	$2.76	$2.61	$2.49	74
	Male Right Angle								
Cable Connectors		Compression	PE-B159, 1855A, Mini 59	PE44579	$14.86	$14.12	$13.37	$12.78	75
		Crimp/Solder	RG59*, RG62*, RG71	PE44322	$8.93	$8.48	$8.04	$7.68	76
			RG6-CATV	PE44320	$10.65	$10.12	$9.59	$9.16	77
		Twist	RG59*, RG62*, RG71	PE44323	$6.81	$6.47	$6.13	$5.86	78
	Female								
PCB Mount		Solder	Thru Hole with .320 inch x .091 inch Hole Spacing	PE44331	$2.54	$2.41	$2.29	$2.18	79
	Female, Bulkhead Mount								
Cable Connectors		Crimp/Solder	PE-B159, 1855A, Mini 59 with .480 inch D Hole	PE44585	$8.16	$7.75	$7.34	$7.02	80
			RG179, RG187 with .380 inch DD Hole	PE45504	$7.62	$7.32	$7.09	$6.93	81
			RG59*, RG62*, RG71	PE45552	$5.92	$5.62	$5.33	$5.09	82
			RG6-CATV	PE44324	$9.89	$9.40	$8.90	$8.51	83

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

75 Ohm F Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
PCB Mount		Solder	Thru Hole with .340 inch x .091 inch Hole Spacing	PE44332	$6.56	$6.23	$5.90	$5.64	84
Terminal			Tab with .380 inch DD Hole	PE44327	$1.92	$1.82	$1.73	$1.65	85
	Female, 4 Hole Flange Mount								
Terminal		Solder	Pin with .500 inch Hole Spacing	PE44329	$11.04	$10.49	$9.94	$9.49	86
	Female, Thread-In								
Terminal		Solder	Pin with .380 inch Diameter	PE44330	$3.04	$2.89	$2.74	$2.61	87
	Female Right Angle								
PCB Mount		Solder	Thru Hole with .320 inch x .091 inch Hole Spacing	PE44333	$7.85	$7.46	$7.07	$6.75	88
	Female Right Angle, Bulkhead Mount								
PCB Mount		Solder	Surface Mount	PE44895	$16.94	$16.09	$15.25	$14.57	89
			Thru Hole with .350 inch D Hole	PE44334	$9.59	$9.11	$8.63	$8.25	90

75 Ohm MCX Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG179, RG187	PE44298	$16.17	$15.36	$14.55	$13.91	91
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG179, RG187	PE45086	$19.56	$18.58	$17.60	$16.82	92
	Jack								
Cable Connectors		Crimp/Solder	RG179, RG187	PE44300	$31.61	$30.03	$28.45	$27.18	93
PCB Mount		Solder	.072 inch End Launch	PE45211	$14.69	$13.96	$13.22	$12.63	94
	Jack Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .055 inch Hole Spacing	PE44304	$19.74	$18.75	$17.77	$16.98	95

75 Ohm Mini SMB Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	PE-B159, 1855A, Mini 59	PE44588	$24.85	$23.61	$22.37	$21.37	96
			RG179, RG187	PE4993	$20.13	$19.12	$18.12	$17.31	97
			RG59*, RG62*, RG71	PE4994	$32.00	$30.72	$29.76	$29.12	98

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

75 Ohm Mini SMB Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG179, RG187	PE4995	$23.35	$22.18	$21.02	$20.08	99
			RG59*, RG62*, RG71	PE4996	$27.95	$26.55	$25.16	$24.04	1
	Jack								
Cable Connectors		Crimp/Solder	Mini 59, PE-B159	PE44590	$29.52	$28.04	$26.57	$25.39	2
PCB Mount		Solder	.062 inch End Launch	PE44131	$27.80	$26.41	$25.02	$23.91	3
			Thru Hole with .200 inch x .055 inch Hole Spacing	PE4997	$19.39	$18.42	$17.45	$16.68	4
	Jack, 2 Hole Flange Mount								
Terminal		Solder	Solder Cup with .328 inch Hole Spacing	PE44141	$27.16	$25.80	$24.44	$23.36	5
	Jack Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .055 inch Hole Spacing	PE4998	$27.30	$25.94	$24.57	$23.48	6
	Jack Right Angle, Bulkhead Mount								
PCB Mount		Solder	Thru Hole with .177 inch D Hole	PE44128	$27.95	$26.55	$25.16	$24.04	7

75 Ohm N Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	RG11*, RG144*, RG216*	PE4509	$39.01	$37.45	$36.28	$35.50	8
			RG179, RG187	PE4513	$23.40	$22.23	$21.06	$20.12	9
			RG59*, RG62*, RG71	PE4511	$26.27	$24.96	$23.64	$22.59	10
			RG6	PE4507	$25.80	$24.51	$23.22	$22.19	11
		Crimp/ Non-Solder Contact	LMR-400-75	EZ-400-NMH-75-X	$36.99	$36.99	$36.99	$36.99	12
		Crimp/Solder	RG11*, RG144*, RG216*	PE4510	$27.79	$26.40	$25.01	$23.90	13
			RG179, RG187	PE4656	$40.69	$38.66	$36.62	$34.99	14
			RG59*, RG62*, RG71	PE4512	$27.00	$25.65	$24.30	$23.22	15
			RG6	PE4508	$27.28	$25.92	$24.55	$23.46	16
	Male, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .718 inch Hole Spacing	PE4504	$46.66	$44.33	$41.99	$40.13	17
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG11*, RG144*, RG216*	PE4502	$58.01	$55.69	$53.95	$52.79	18
	Female								
Cable Connectors		Clamp/Solder	RG59*, RG62*, RG71	PE4516	$44.23	$42.02	$39.81	$38.04	19
			RG6	PE4514	$54.32	$52.15	$50.52	$49.43	20

*** Fits MIL-C-17 and equivalent cable versions only**

Connectors

See Our Website For Current Pricing & Real-Time Stock Availability!

75 Ohm N Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, Bulkhead Mount								
Terminal		Solder	Solder Cup with .380 inch Diameter	PE4506	$20.70	$19.67	$18.63	$17.80	21
			Solder Cup with .640 inch DD Hole	PE4505	$31.30	$29.74	$28.17	$26.92	22
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .718 inch Hole Spacing	PE4503	$19.39	$18.42	$17.45	$16.68	23

75 Ohm RCA Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Compression	Mini 59, PE-B159	PE44576	$7.85	$7.46	$7.07	$6.75	24
			PE-B159, 1855A, Mini 59	PE44574	$14.61	$13.88	$13.15	$12.56	25
		Crimp/Solder	1505A	PE44624	$16.55	$15.72	$14.90	$14.23	26
			1694A	PE44623	$13.50	$12.83	$12.15	$11.61	27
			Mini 59, PE-B159	PE44622	$16.55	$15.72	$14.90	$14.23	28
			PE-B159	PE44583	$15.64	$14.86	$14.08	$13.45	29
	Male Right Angle								
Cable Connectors		Compression	Mini 59, PE-B159	PE44580	$19.73	$18.74	$17.76	$16.97	30
	Female, Bulkhead Mount								
Cable Connectors		Crimp/Solder	PE-B159, 1855A, Mini 59 with .480 inch D Hole	PE44586	$19.91	$18.91	$17.92	$17.12	31

75 Ohm SMB Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Clamp/Solder	RG179, RG187	PE4257	$27.75	$26.36	$24.98	$23.87	32
			RG59*, RG62*, RG71	PE4203	$21.62	$20.54	$19.46	$18.59	33
		Crimp/Solder	RG179, RG187	PE4248	$22.54	$21.41	$20.29	$19.38	34
			RG59*, RG62*, RG71	PE4472	$27.77	$26.38	$24.99	$23.88	35
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4368	$21.35	$20.50	$19.86	$19.43	36
	Plug, Bulkhead Mount								
Terminal		Solder	Solder Cup with .295 inch D Hole	PE4290	$68.46	$65.04	$61.61	$58.88	37
	Plug Right Angle								
Cable Connectors		Clamp/Solder	RG59*, RG62*	PE4264	$43.60	$41.42	$39.24	$37.50	38
		Crimp/Solder	PE-B150, RG180, RG195	PE4161	$48.78	$46.83	$45.37	$44.39	39
			RG179, RG187	PE4251	$30.27	$28.76	$27.24	$26.03	40

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

75 Ohm SMB Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Jack								
Cable Connectors		Clamp/Solder	RG179, RG187	PE4928	$48.92	$46.47	$44.03	$42.07	41
			RG59*, RG62*	PE4272	$37.62	$35.74	$33.86	$32.35	42
		Crimp/Solder	PE-B150, RG180, RG195	PE4163	$22.92	$21.77	$20.63	$19.71	43
			RG179, RG187	PE44872	$39.20	$37.24	$35.28	$33.71	44
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4110	$24.71	$23.47	$22.24	$21.25	45
	Jack, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG180, RG195 with .285 inch D Hole	PE4281	$29.23	$27.77	$26.31	$25.14	46
		Crimp/Solder	RG179, RG187 with .285 inch D Hole	PE4255	$52.36	$49.74	$47.12	$45.03	47
Terminal		Solder	Solder Cup with .295 inch D Hole	PE4172	$19.59	$18.61	$17.63	$16.85	48
			Solder Cup with .317 inch Diameter	PE4168	$18.68	$17.75	$16.81	$16.06	49
	Jack Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4179	$26.06	$24.76	$23.45	$22.41	50

75 Ohm SMB Positive Snap Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG179, RG187	PE44443	$34.83	$33.09	$31.35	$29.95	51
			RG59*, RG62*	PE44442	$24.62	$23.39	$22.16	$21.17	52
	Plug Right Angle								
Cable Connectors		Crimp/Solder	RG179, RG187	PE44445	$38.31	$36.39	$34.48	$32.95	53
			RG180, RG195	PE44446	$51.70	$49.12	$46.53	$44.46	54

75 Ohm SMC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Clamp/Solder	RG179, RG187	PE4259	$48.92	$46.47	$44.03	$42.07	55
			RG59*, RG62*, RG71	PE4258	$52.09	$49.49	$46.88	$44.80	56
		Crimp/Solder	PE-B150, RG180, RG195	PE4158	$29.29	$27.83	$26.36	$25.19	57
			RG179, RG187	PE4249	$24.28	$23.07	$21.85	$20.88	58
			RG59*, RG62*, RG71	PE4658	$30.45	$28.93	$27.41	$26.19	59
	Plug, Bulkhead Mount								
Terminal		Solder	Solder Cup with .295 inch D Hole	PE4291	$50.40	$47.88	$45.36	$43.34	60

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

75 Ohm SMC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug Right Angle								
Cable Connectors		Clamp/Solder	RG59*, RG62*	PE4266	$32.89	$31.25	$29.60	$28.29	61
		Crimp/Solder	RG180, RG195	PE4162	$40.63	$38.60	$36.57	$34.94	62
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4293	$49.99	$47.49	$44.99	$42.99	63
	Jack								
Cable Connectors		Clamp/Solder	RG180, RG195	PE4275	$35.78	$33.99	$32.20	$30.77	64
			RG59*, RG62*	PE4274	$42.62	$40.49	$38.36	$36.65	65
		Crimp/Solder	RG179, RG187	PE4254	$38.64	$37.09	$35.94	$35.16	66
			RG180, RG195	PE4164	$32.82	$31.51	$30.52	$29.87	67
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4176	$23.17	$22.24	$21.55	$21.08	68
	Jack, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG179, RG187	PE4906	$48.12	$45.71	$43.31	$41.38	69
			RG180, RG195 with .285 inch D Hole	PE4283	$31.88	$30.29	$28.69	$27.42	70
		Crimp/Solder	RG179, RG187 with .285 inch D Hole	PE4256	$37.93	$36.03	$34.14	$32.62	71
			RG180, RG195 with .177 inch D Hole	PE45205	$37.54	$34.91	$32.28	$30.03	72
Terminal		Solder	Solder Cup with .295 inch D Hole	PE4169	$50.05	$47.55	$45.05	$43.04	73
			Solder Cup with .295 inch D Hole	PE4173	$34.96	$33.21	$31.46	$30.07	74
	Jack Right Angle								
PCB Mount		Solder	Thru Hole with .200 inch x .067 inch Hole Spacing	PE4180	$44.20	$41.99	$39.78	$38.01	75

75 Ohm TNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	RG11*, RG144*, RG216*	PE44163	$64.46	$61.24	$58.01	$55.44	76
			RG179, RG187	PE44167	$20.42	$19.40	$18.38	$17.56	77
			RG59*	PE44165	$20.42	$19.40	$18.38	$17.56	78
			RG6	PE44161	$28.89	$27.73	$26.87	$26.29	79
		Crimp/Solder	RG11*, RG144*	PE44164	$46.82	$44.48	$42.14	$40.27	80
			RG179, RG187	PE44168	$20.80	$19.76	$18.72	$17.89	81
			RG59*, RG62*	PE44166	$20.42	$19.40	$18.38	$17.56	82
			RG6	PE44162	$23.60	$22.42	$21.24	$20.30	83
	Male Right Angle								
Cable Connectors		Clamp/Solder	RG179, RG187	PE44172	$60.47	$57.45	$54.42	$52.00	84
			RG59*, RG62*, RG71	PE44171	$63.50	$60.33	$57.15	$54.61	85
	Female, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG11*, RG216* with .480 inch D Hole	PE44174	$50.61	$48.08	$45.55	$43.52	86
			RG179, RG187 with .480 inch D Hole	PE44176	$51.78	$49.19	$46.60	$44.53	87
			RG6 with .480 inch D Hole	PE44173	$48.36	$45.94	$43.52	$41.59	88
Terminal		Solder	Solder Cup with .410 inch D Hole	PE44177	$24.28	$23.07	$21.85	$20.88	89
			Solder Cup with .480 inch D Hole	PE44181	$30.42	$28.90	$27.38	$26.16	90

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

75 Ohm TNC Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .500 inch Threaded Hole Spacing	PE44178	$22.60	$21.47	$20.34	$19.44	91

BNC Twinax Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Clamp/Solder	RG108, 78 Ohm Twinax	PE4236	$31.29	$29.73	$28.16	$26.91	92
		Crimp/Solder	RG108, 78 Ohm Twinax	PE4234	$23.86	$22.67	$21.47	$20.52	93
	Jack								
Cable Connectors		Clamp/Solder	RG108, 78 Ohm Twinax	PE4237	$39.15	$37.19	$35.24	$33.67	94
		Crimp/Solder	RG108, 78 Ohm Twinax	PE4235	$45.15	$42.89	$40.64	$38.83	95
PCB Mount		Solder	Thru Hole with .687 inch x .500 inch Hole Spacing	PE44115	$35.26	$33.85	$32.79	$32.09	96
	Jack, Bulkhead Mount								
Cable Connectors		Clamp/Solder	RG108, 78 Ohm Twinax with .480 inch D Hole	PE44114	$54.40	$51.68	$48.96	$46.78	97
Terminal		Solder	Solder Cup with .350 inch D Hole	PE4238	$25.29	$24.03	$22.76	$21.75	98
	Jack, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .500 inch Threaded Hole Spacing	PE4324	$49.09	$46.64	$44.18	$42.22	99
	Jack Right Angle								
PCB Mount		Solder	Thru Hole with .687 inch x .500 inch Hole Spacing	PE44116	$54.16	$51.45	$48.74	$46.58	1

3/4”-20 Twinax Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Male								
Cable Connectors		Clamp/Solder	PE-S330	PE4104	$32.50	$30.88	$29.25	$27.95	2
	Female								
Cable Connectors		Clamp/Solder	PE-S330	PE4346	$28.69	$27.26	$25.82	$24.67	3

* Fits MIL-C-17 and equivalent cable versions only

See Our Website For Current Pricing & Real-Time Stock Availability!

3/4”-20 Twinax Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Female, Bulkhead Mount								
Terminal		Solder	Solder Cup with .720 inch D Hole	PE4105	$29.81	$28.32	$26.83	$25.64	4
	Female, 4 Hole Flange Mount								
Terminal		Solder	Solder Cup with .718 inch Hole Spacing	PE4347	$35.44	$33.67	$31.90	$30.48	5

Banana Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	RG55, RG142, RG223, RG400	PE4089	$11.48	$10.91	$10.33	$9.87	6
			RG188-DS, RG316-DS	PE45164	$16.95	$16.10	$15.26	$14.58	7

Double Banana Connectors

Connection Method	Product Image	Attachment Cable/Contact	Coax Type / Termination Type	Model No.	PRICE 1-24	25-49	50-99	100 +	ROW
	Plug								
Cable Connectors		Crimp/Solder	PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, .195 inch	PE4301	$12.04	$11.44	$10.84	$10.35	8
			RG174, RG316, RG188, .100 inch, PE-B100, PE-C100, LMR-100	PE44145	$15.67	$14.89	$14.10	$13.48	9

CONNECTOR DUST CAPS

Non-Shorting Caps

Connector	Gender	Compatible With	Chain	Model No	1-24	25-49	50-99	100+	ROW
7/16 DIN	Male	50 Ohm	Yes	PE6057	$49.22	$46.76	$44.30	$42.33	10
	Female		Yes	PE6058	$58.56	$55.63	$52.70	$50.36	11
BNC	Male		Yes	PE6013	$10.45	$9.93	$9.41	$8.99	12
			No	PE6014	$5.85	$5.56	$5.27	$5.03	13
	Female		Yes	PE6015	$8.53	$8.10	$7.68	$7.34	14
			No	PE6108	$15.55	$14.77	$14.00	$13.37	15
C	Male		Yes	PE6046	$31.72	$30.13	$28.55	$27.28	16
			No	PE6109	$34.67	$32.94	$31.20	$29.82	17
	Female		Yes	PE6110	$32.14	$30.53	$28.93	$27.64	18
			No	PE6111	$24.30	$23.09	$21.87	$20.90	19
F	Male		No	PE6240	$4.25	$4.04	$3.83	$3.66	20
HN			Yes	PE6059	$32.65	$31.02	$29.39	$28.08	21
			No	PE6113	$24.08	$22.88	$21.67	$20.71	22
	Female		Yes	PE6114	$31.97	$30.37	$28.77	$27.49	23
			No	PE6115	$32.62	$30.99	$29.36	$28.05	24
N	Male		Yes	PE6016	$8.65	$8.22	$7.79	$7.44	25
			No	PE6017	$9.54	$9.06	$8.59	$8.20	26
	Female		Yes	PE6018	$13.03	$12.38	$11.73	$11.21	27
			No	PE6116	$11.27	$10.71	$10.14	$9.69	28

*** Fits MIL-C-17 and equivalent cable versions only**

See Our Website For Current Pricing & Real-Time Stock Availability!

Non-Shorting Caps

Connector	Gender	Compatible With	Chain	Model No	1-24	25-49	50-99	100+	ROW
SC	Male	50 Ohm	Yes	PE6117	$46.82	$44.48	$42.14	$40.27	29
	Female		Yes	PE6118	$39.67	$37.69	$35.70	$34.12	30
SMA	Male		Yes	PE6019	$20.50	$19.48	$18.45	$17.63	31
			No	PE6024	$4.51	$4.28	$4.06	$3.88	32
	Female		Yes	PE6119	$26.74	$25.40	$24.07	$23.00	33
			No	PE6120	$10.53	$10.00	$9.48	$9.06	34
SMB	Plug		Yes	PE6121	$27.67	$26.29	$24.90	$23.80	35
		75 Ohm	Yes	PE6125	$43.51	$41.33	$39.16	$37.42	36
	Jack	50 Ohm	Yes	PE6122	$23.77	$22.58	$21.39	$20.44	37
SMC	Plug	75 Ohm	Yes	PE6126	$40.02	$38.02	$36.02	$34.42	38
	Jack	50 Ohm	Yes	PE6124	$18.54	$17.61	$16.69	$15.94	39
SSMA	Male		No	PE6020	$21.26	$20.20	$19.13	$18.28	40
TNC			Yes	PE6023	$11.84	$11.25	$10.66	$10.18	41
			No	PE6144	$11.04	$10.49	$9.94	$9.49	42
	Female		Yes	PE6021	$14.56	$13.83	$13.10	$12.52	43

Shorting Caps

Connector	Gender	Compatible With	Chain	Model No	1-24	25-49	50-99	100+	ROW
2.4mm	Male	50 Ohm	Yes	PE6194	$69.19	$66.42	$64.35	$62.96	44
	Female		Yes	PE6195	$83.32	$79.15	$74.99	$71.66	45
			No	PE6193	$75.55	$71.77	$68.00	$64.97	46
BNC	Male		Yes	PE6127	$27.02	$25.67	$24.32	$23.24	47
			No	PE6012	$9.25	$8.79	$8.33	$7.96	48
	Female		Yes	PE6128	$30.82	$29.28	$27.74	$26.51	49
			No	PE6030	$17.30	$16.44	$15.57	$14.88	50
N	Male		Yes	PE6129	$33.68	$32.00	$30.31	$28.96	51
			No	PE6022	$25.04	$23.79	$22.54	$21.53	52
	Female		Yes	PE6130	$54.39	$51.67	$48.95	$46.78	53
			No	PE6031	$12.08	$11.48	$10.87	$10.39	54
SMA	Male		Yes	PE6131	$32.91	$31.26	$29.62	$28.30	55
			No	PE6006	$25.83	$24.54	$23.25	$22.21	56
	Female		Yes	PE6132	$37.81	$35.92	$34.03	$32.52	57
			Yes	PE6251	$27.86	$26.75	$25.91	$25.35	58
			No	PE6007	$27.31	$25.94	$24.58	$23.49	59
TNC	Male		Yes	PE6134	$30.81	$29.27	$27.73	$26.50	60
			No	PE6133	$27.25	$25.89	$24.53	$23.44	61
	Female		Yes	PE6136	$34.03	$32.33	$30.63	$29.27	62
			No	PE6135	$25.74	$24.45	$23.17	$22.14	63

See Our Website For Current Pricing & Real-Time Stock Availability!

Single Directional

1.85mm Connectors

Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1	2-4	5-9	10+	ROW
1,000-67,000	10	20 Watt	8	PE2CP1127-10	$6,448.93	$6,190.97	$5,933.02	$5,675.06	1
	20			PE2CP1127-20	$6,545.46	$6,283.64	$6,021.82	$5,760.00	

2.4mm Connectors

Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1	2-4	5-9	10+	ROW
2,000-52,000	10	20 Watt	10	PE2CP1134-10	$3,440.00	$3,302.40	$3,164.80	$3,027.20	2
18,000-50,000	20		8	PE2CP1135-20	$3,363.15	$3,228.62	$3,094.10	$2,959.57	3

2.92mm Connectors

Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1	2-4	5-9	10+	ROW
1,000-40,000	10	20 Watt		PE2CP1122-10	$2,266.17	$2,175.52	$2,084.88	$1,994.23	
	20	30 Watt		PE2CP1122-20	$2,076.96	$1,993.88	$1,910.80	$1,827.72	4
	30			PE2CP1122-30	$2,224.18	$2,135.21	$2,046.25	$1,957.28	
2,000-40,000	10		10	PE2CP1133-10	$1,926.07	$1,849.03	$1,771.98	$1,694.94	
	20			PE2CP1133-20	$1,699.00	$1,631.04	$1,563.08	$1,495.12	5
	30			PE2CP1133-30	$1,926.07	$1,849.03	$1,771.98	$1,694.94	
6,000-26,500	10		12	PE2CP1129-10	$1,505.00	$1,444.80	$1,384.60	$1,324.40	6
6,000-40,000			10	PE2CP1124-10	$1,812.70	$1,740.19	$1,667.68	$1,595.18	7
	20			PE2CP1124-20	$1,744.67	$1,674.88	$1,605.10	$1,535.31	
8,000-40,000	10			PE2CP1125-10	$1,684.18	$1,616.81	$1,549.45	$1,482.08	
	20			PE2CP1125-20	$1,709.39	$1,641.01	$1,572.64	$1,504.26	8
	30		10	PE2CP1125-30	$1,709.39	$1,641.01	$1,572.64	$1,504.26	
8,000-43,500	15			PE2CP1125-15	$1,684.18	$1,616.81	$1,549.45	$1,482.08	
18,000-40,000	6		10	PE2CP1126-6	$1,503.93	$1,443.77	$1,383.62	$1,323.46	
	10		12	PE2CP1126-10	$1,526.45	$1,465.39	$1,404.33	$1,343.28	9
	20			PE2CP1126-20	$1,585.97	$1,522.53	$1,459.09	$1,395.65	

4.1/9.5 Mini DIN Connectors

Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
698-2,700	6	200 Watt	20	PE2CP1059	$515.27	See Web for Volume Pricing			10
	10			PE2CP1063	$511.53				11
	15			PE2CP1067	$590.56				12
	20			PE2CP1071	$511.53				13
	30			PE2CP1075	$511.53				14

4.3-10 Connectors

Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1-4	5-9	10-24	25+	ROW
380-2,700	30	200 Watt	20	PE2CP1076	$560.08	$532.08	$504.07	$481.67	15
698-2,700	6			PE2CP1060	$560.08	$532.08	$504.07	$481.67	16
	10			PE2CP1064	$560.08	$532.08	$504.07	$481.67	17

4.3-10 Connectors

Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1-4	5-9	10-24	25+	ROW
698-2,700	15	200 Watt	20	PE2CP1068	$560.08	$532.08	$504.07	$481.67	18
	20			PE2CP1072	$560.08	$532.08	$504.07	$481.67	19

7/16 DIN Connectors

Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1-4	5-9	10-24	25+	ROW
698-2,700	6	200 Watt	20	PE2CP1058	$541.41	$514.34	$487.27	$465.61	20
	10			PE2CP1062	$634.39	$602.67	$570.95	$545.58	21
	15			PE2CP1066	$634.39	$602.67	$570.95	$545.58	22
	20			PE2CP1070	$570.95	$542.40	$513.86	$491.02	23
	30			PE2CP1074	$570.95	$542.40	$513.86	$491.02	24

N Connectors

Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
500-2,000	30	600 Watt	18	PE2240-30	$1,272.96		See Web for Volume Pricing		25
698-2,700	6	200 Watt	20	PE2CP1057	$511.89				26
	10			PE2CP1061	$568.79				27
	15			PE2CP1065	$568.79				28
	20			PE2CP1069	$589.50				29
	30			PE2CP1073	$589.50				30
800-2,500	6	60 Watt		PE2CP1023-6	$554.03				31
	10			PE2CP1023-10	$568.68				
	20			PE2CP1023-20	$555.20				
	30			PE2CP1023-30	$555.66				
1,000-2,000		600 Watt	28	PE2226-30	$1,375.05				32
1,000-4,000			15	PE2228A-30	$1,919.27				33
1,000-8,000				PE2239-30	$2,071.28				34
1,000-11,000	35		20	PE2236-35	$2,768.59				35
4,000-8,000	30		18	PE2230-30	$1,424.39				36
4,000-12,000			15	PE2235-30	$1,775.50				37
4,000-18,000	10	50 Watt	12	PE2CP1114-10	$633.72				38
	20			PE2CP1114-20	$624.36				

SMA Connectors

Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
500-1,000	10	50 Watt	25	PE2200-10	$432.67		See Web for Volume Pricing		39
	20			PE2200-20	$481.30				
	30			PE2200-30	$484.36				
500-2,000	6		20	PE2CP003-6	$426.06				40
			23	PE2208-6	$553.89				41
	10		20	PE2CP003-10	$299.56				42
			23	PE2208-10	$567.06				43
	20		20	PE2CP003-20	$318.05				44
			23	PE2208-20	$583.41				45
500-3,000	10		18	PE2242-10	$304.42				46
	20			PE2242-20	$304.42				
				PE2242A-20	$304.42				47
	30			PE2242-30	$304.42				48
500-18,000	10	30 Watt		PE2243-10	$1,556.56				49
	16			PE2243-16	$1,533.55				
	20			PE2243-20	$1,618.09				
	30			PE2243-30	$1,556.56				

SMA Connectors

Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
600-4,000	10	50 Watt	18	PE2213-10	$815.06	See Web for Volume Pricing	50
700-2,700	6		20	PE2CP002-6	$282.77		51
	10			PE2CP002-10	$278.60		
	20			PE2CP002-20	$273.39		
800-2,200	10			PE2CP025-10	$236.02		52
800-2,500	6			PE2CP1024-6	$542.20		53
	10			PE2CP1025-10	$568.79		54
	20			PE2CP1025-20	$507.94		
	30			PE2CP1024-30	$555.66		55
1,000-2,000	10		25	PE2201-10	$397.17		56
	20			PE2CP1108	$186.16		57
	30			PE2201-30	$403.58		58
1,000-4,000	6		20	PE2CP005-6	$235.09		59
			23	PE2209-6	$555.59		60
	10		20	PE2CP005-10	$227.16		61
				PE2CP1102	$202.32		62
	20			PE2CP005-20	$241.22		63
			23	PE2209-20	$605.44		64
2,000-4,000	6		22	PE2202-6	$396.79		65
	30			PE2202-30	$416.48		
2,000-8,000	6		20	PE2CP004-6	$305.25		66
				PE2210-6	$528.94		67
	10			PE2CP004-10	$328.21		68
				PE2210-10	$501.88		69
	20			PE2CP004-20	$321.90		70
				PE2210-20	$554.23		71
2,000-18,000	6	4 Watt	12	PE2215-6	$1,962.88		72
	10	50 Watt		PE2CP000-10	$674.65		73
				PE2CP1103	$483.70		74
		25 Watt		PE2215-10	$2,214.16		75
	20	50 Watt		PE2CP000-20	$711.20		76
	30		10	PE2CP000-30	$691.26		
2,000-18,400	20	25 Watt	12	PE2215-20	$1,892.04		77
2,600-5,200	10	50 Watt	20	PE2203-10	$569.83		78
	20			PE2CP1109	$196.50		79
				PE2203-20	$581.57		80
	30			PE2203-30	$596.52		
4,000-8,000	6			PE2204-6	$379.97		81
	10			PE2204-10	$303.48		
	20			PE2204-20	$380.97		
	30			PE2204-30	$416.07		
4,000-12,400	6		17	PE2211-6	$589.50		82
	10			PE2211-10	$539.32		
	20			PE2211-20	$568.53		
4,000-18,000	6		12	PE2CP1100	$415.69		83
	10			PE2CP1104	$415.69		84
	20			PE2CP1110	$409.55		85
6,000-18,000	10		10	PE2CP001-10	$522.57		86
	20		12	PE2CP001-20	$522.57		
6,000-26,500	10	30 Watt		PE2CP1120-10	$1,132.52		87
	30		13	PE2CP1120-30	$1,073.93		
6,000-26,600	20			PE2CP1120-20	$1,132.52		
7,000-12,400	6	50 Watt	17	PE2CP1101	$327.63		88
	10			PE2CP1105	$332.55		89
	20			PE2205-20	$534.52		90
	30			PE2205-30	$533.55		
7,000-16,000			12	PE2CP1112	$374.12		91
7,000-18,000	10		15	PE2CP1106	$340.10		92
7,500-16,000	6		12	PE2206-6	$513.94		93
	10		15	PE2CP1107	$320.06		94
12,400-18,000	6	4 Watt		PE2207-6	$608.13		95
	10	50 Watt		PE2207-10	$526.36		
	20			PE2CP1111	$370.34		96
	30			PE2207-30	$544.16		97
18,000-26,000		30 Watt	13	PE2CP1121-30	$937.16		98

Dual Directional

N Connectors

Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1	2-4	5-9	10+	ROW
2-30	50	2500 Watt	22	PE2CP1000	$3,299.00	$3,167.04	$3,035.08	$2,903.12	99
20-500		500 Watt	20	PE2CP1002	$1,911.77	$1,835.30	$1,758.83	$1,682.36	1
		1000 Watt		PE2CP1003	$2,554.72	$2,452.53	$2,350.34	$2,248.15	2
20-1,000		500 Watt		PE2CP1005	$1,898.81	$1,822.86	$1,746.91	$1,670.95	3
80-1,000				PE2CP1007	$1,860.06	$1,785.66	$1,711.26	$1,636.85	4
		1000 Watt		PE2CP1008	$2,652.21	$2,546.12	$2,440.03	$2,333.94	5
		200 Watt		PE2CP1021	$1,554.52	$1,492.34	$1,430.16	$1,367.98	6
100-500	40	500 Watt		PE2CP1010	$1,743.84	$1,674.09	$1,604.33	$1,534.58	7
		1000 Watt		PE2CP1020	$2,449.78	$2,351.79	$2,253.80	$2,155.81	8
500-2,500		200 Watt	18	PE2CP1011	$1,118.66	$1,073.91	$1,029.17	$984.42	9
		500 Watt	20	PE2CP1012	$1,800.16	$1,728.15	$1,656.15	$1,584.14	10
500-3,000		200 Watt	18	PE2CP1013	$1,937.61	$1,860.11	$1,782.60	$1,705.10	11
800-2,500		500 Watt	20	PE2CP1015	$1,899.00	$1,823.04	$1,747.08	$1,671.12	12
800-4,200		200 Watt		PE2CP1016	$2,220.63	$2,131.80	$2,042.98	$1,954.15	13
2,000-6,000	20		15	PE2CP1019	$1,543.00	$1,481.28	$1,419.56	$1,357.84	14

SC Connectors

Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1	2-4	5-9	10+	ROW
20-1,000	50	1000 Watt	20	PE2CP1006	$2,955.39	$2,837.17	$2,718.96	$2,600.74	15
800-4,200	40	600 Watt	18	PE2CP1017	$3,039.00	$2,917.44	$2,795.88	$2,674.32	16

SMA Connectors

Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
20-520	50	200 Watt	20	PE2CP1001	$1,222.63	See Web for Volume Pricing			17
20-1,000				PE2CP1004	$1,533.92				18
100-500	40			PE2CP1009	$1,403.83				19
500-1,000	10	10 Watt	22	PE2217-10	$821.89				20
	20	50 Watt		PE2217-20	$835.13				21
	30			PE2217-30	$803.00				22
800-2,500	40	200 Watt	20	PE2CP1014	$1,166.92				23
1,000-2,000	10	10 Watt	22	PE2218-10	$803.00				24
	20	50 Watt		PE2218-20	$803.00				25
	30			PE2218-30	$813.90				26
2,000-4,000	20		20	PE2219-20	$924.81				27
2,000-6,000		100 Watt	16	PE2CP1018	$1,155.09				28
2,000-8,000		50 Watt	20	PE2CP1113	$672.63				29
2,600-5,200	10	10 Watt	18	PE2220-10	$842.15				30
	20	50 Watt		PE2220-20	$743.13				31
	30			PE2220-30	$757.13				32
4,000-8,000	10	10 Watt		PE2221-10	$818.14				33
7,000-12,400	30	50 Watt	16	PE2222-30	$803.00				34
8,000-16,000	10	10 Watt	15	PE2223-10	$803.00				35
	20	50 Watt		PE2223-20	$835.13				36
	30			PE2223-30	$834.18				37
12,400-18,000	20			PE2224-20	$827.81				38

90 Degree Hybrids

2.92mm Connectors

Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Minimum Isolation (dB)	Model No	1-4	5-9	10-24	25+	ROW
2,000-40,000			10	PE2CP1150	$1,998.76	$1,898.82	$1,798.88	$1,718.93	39
5,000-26,500			14	PE2CP1147	$999.38	$949.41	$899.44	$859.47	40
8,000-43,500		20 Watt	12	PE2CP1149	$1,499.07	$1,424.12	$1,349.16	$1,289.20	41
10,000-26,500			15	PE2CP1146	$999.38	$949.41	$899.44	$859.47	42
20,000-40,000			12	PE2CP1148	$1,499.07	$1,424.12	$1,349.16	$1,289.20	43

Pin Connectors



Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Minimum Isolation (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
20-1,000		50 Watt	16	PE2CP1026	$852.74				64
		150 Watt		PE2CP1027	$950.99				65
80-1,000		250 Watt		PE2CP1028	$667.47				66
100-500		150 Watt		PE2CP1029	$312.04				67
130-180		200 Watt	20	PE2CP1032	$98.45				68
		800 Watt	18	PE2CP1033	$411.15				69
225-400		250 Watt	20	PE2CP1034	$115.38				70
225-450		400 Watt		PE2CP1035	$160.89				71
		800 Watt		PE2CP1036	$411.15				72
400-1,000		200 Watt	19	PE2CP1037	$82.94				73
		400 Watt	20	PE2CP1038	$122.42				74
		800 Watt		PE2CP1039	$478.85				75
500-2,500		150 Watt	18	PE2CP1040	$192.27				76
		200 Watt	17	PE2CP1041	$292.60				77
		300 Watt		PE2CP1042	$422.76				78
500-3,000		125 Watt	18	PE2CP1043	$195.15				79
		200 Watt	17	PE2CP1044	$354.56				80
800-1,600			20	PE2CP1045	$95.17				81
800-2,500			18	PE2CP1046	$150.22				82
800-2,700		400 Watt	17	PE2CP1047	$705.80				83
960-1,220		125 Watt	20	PE2CP1048	$87.09				84
1,000-2,000		200 Watt		PE2CP1049	$85.46				85
		400 Watt		PE2CP1050	$112.80				86
		1000 Watt	18	PE2CP1051	$478.85				87
1,000-3,000		150 Watt		PE2CP1052	$102.03				88
		450 Watt	16	PE2CP1053	$181.39				89
1,000-4,200		80 Watt	18	PE2CP1054	$165.44				90
2,000-4,000		100 Watt		PE2CP1055	$87.09				91
2,000-6,000				PE2CP1056	$85.54				92

SMA Connectors

Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Minimum Isolation (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
500-1,000		50 Watt	22	PE2CP011	$261.79				44
				PE2CP1140	$499.69				45
		100 Watt	28	PE2050	$551.97				46
800-3,000		50 Watt	20	PE2CP021	$388.25				47
1,000-2,000			22	PE2CP013	$261.79				48
1,000-18,000			15	PE2CP1144	$636.28				49
1,400-2,500			23	PE2CP1145	$556.33				50
2,000-4,000			22	PE2CP017	$261.79				51
				PE2052	$478.74				52
2,000-8,000		30 Watt	17	PE2058	$543.95				53
2,000-18,000		50 Watt	15	PE2CP023	$1,070.38				54
4,000-8,000			18	PE2CP019	$261.79				55
4,000-12,400	4	100 Watt		PE2059	$813.41				56
4,000-18,000		50 Watt	16	PE2CP1143	$556.33				57
5,000-10,000			20	PE2CP1141	$499.69				58

SMA Connectors

Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Minimum Isolation (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
6,000-12,400	3	100 Watt	17	PE2055	$601.31		See Web for Volume Pricing		59
6,000-18,000		30 Watt	16	PE2CP1142	$586.30				60
7,000-18,000			18	PE2CP1022	$691.33				61
7,500-16,000		100 Watt		PE2056A	$584.58				62
12,000-18,000		40 Watt	15	PE2057	$527.79				63

180 Degree Hybrids

2.92mm Connectors

Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Minimum Isolation (dB)	Model No	1-4	5-9	10-24	25+	ROW
26,500-40,000		20 Watt	15	PE2CP1161	$2,085.37	$1,981.10	$1,876.83	$1,793.42	93

SMA Connectors

Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Minimum Isolation (dB)	Model No	1-4	5-9	10-24	25+	ROW
500-1,000		50 Watt	22	PE2CP1151	$689.58	$655.10	$620.62	$593.04	94
1,000-2,000				PE2CP1152	$689.58	$655.10	$620.62	$593.04	95
1,300-2,600		100 Watt	20	PE2CP1153	$689.58	$655.10	$620.62	$593.04	96
1,400-6,000		30 Watt	22	PE2CP1154	$1,345.84	$1,278.55	$1,211.26	$1,157.42	97
2,000-4,000		50 Watt	20	PE2CP1155	$689.58	$655.10	$620.62	$593.04	98
2,000-8,000		30 Watt		PE2CP1157	$899.45	$854.48	$809.51	$773.53	99
2,000-18,000		50 Watt	16	PE2CP1158	$1,399.14	$1,329.18	$1,259.23	$1,203.26	1
4,000-8,000		80 Watt	18	PE2CP1159	$766.19	$727.88	$689.57	$658.92	2
4,000-18,000		50 Watt		PE2CP1160	$1,042.69	$990.56	$938.42	$896.71	3

RF DIPLEXERS

75 Ohm Diplexer F Female with 5 MHz to 390 MHz Low Pass and 650 MHz to 1,000 MHz High Pass PE8DP1001

- 5 - 1000 MHz
- 75 Ohms Impedance
- Typical Return loss 18 dB
- Bidirectional design
- EN 50083-2 Class A Standard

In-stock and available to ship today!

FILTERS

NEW

Low Pass Harmonic Filters: PEHFL0000 - PEHFL0001

- Passband frequency: DC - 6000Hz
- 50 Ohms impedance
- Broadband design: C, L & S Band
- RF input power passband: 50 W
- VSWR: 1.5:1

In-stock and available to ship today!

FILTERS

SMA Connectors

Bandpass Filters

Bandpass Frequency (MHz)	Application	Rejection (MHz)	Max. Insertion Loss (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
824 - 849	GSM	50 dB at 736.5 50 dB at 936.5	2	PE8705	$512.83	See Web for Volume Pricing			4
869 - 894	GSM	50 dB at 781.5 50 dB at 981.5		PE8706	$527.62				5
902 - 928	ISM, RFID	50 dB at 815 50 dB at 1,015		PE8700	$532.82				6
1,000 - 2,000		55 dB at 650 55 dB at 3,000		PE87FL1012	$457.99				7
1,217 - 1,237	GPS L2	50 dB at 1,127 50 dB at 1,327	1	PE8704	$573.83				8
1,565 - 1,585	GPS L1	50 dB at 1,475 50 dB at 1,675	2	PE8703	$532.82				9
1,710 - 1,770	UMTS/AWS	50 dB at 1,490 50 dB at 1,990		PE8710	$527.62				10
1,850 - 1,910	PCS	50 dB at 1,630 50 dB at 2,130		PE8707	$533.35				11
1,920 - 1,980	UMTS	50 dB at 1,700 50 dB at 2,200		PE8709	$560.44				12
1,930 - 1,990	PCS	50 dB at 1,710 50 dB at 2,210		PE8708	$633.14				13
2,000 - 4,000		55 dB at 1,300 55 dB at 6,000		PE87FL1013	$475.84				14
2,110 - 2,170	UMTS/AWS	50 dB at 1,890 50 dB at 2,390		PE8711	$785.12				15
2,400 - 2,500	ISM, WiFi, Bluetooth, Zigbee	50 dB at 2,050 50 dB at 2,850	1	PE8701	$531.76				16
2,500 - 2,700	WIMAX	50 dB at 1,700 50 dB at 3,500		PE8712	$608.36				17
3,300 - 3,700	WiMAX	50 dB at 1,600 50 dB at 5,400		PE8713	$559.17				18
4,400 - 4,950	P2P, Public Safety	30 dB at 5,250 30 dB at 5,850	1	PE8739	$394.23				19
4,900 - 5,900	WiMAX	50 dB at 400 50 dB at 10,400		PE8714	$502.96				20
5,250 - 5,850	P2P, Public Safety	30 dB at 4,400 30 dB at 4,950	1	PE8740	$367.45				21
5,725 - 5,875	ISM, WiFi	50 dB at 5,200 50 dB at 6,400		PE8702	$509.82				22
7,250 - 7,750	VSAT	30 dB at 7,900 30 dB at 8,400	2	PE8741	$423.26				23
7,900 - 8,400	VSAT	30 dB at 7,250 30 dB at 7,750		PE8742	$423.26				24
9,900 - 10,800		50 dB at 8,350 50 dB at 12,350	1	PE87FL1000	$543.60				25
10,550 - 11,800		50 dB at 8,425 50 dB at 13,925		PE87FL1001	$540.93				26
10,700 - 12,200		50 dB at 8,450 50 dB at 14,450		PE87FL1003	$540.93				27

SMA Connectors

Bandpass Filters

Bandpass Frequency (MHz)	Application	Rejection (MHz)	Max. Insertion Loss (dB)	Model No	1-9	10-24	25-49	50+	ROW
11,700 - 12,800		50 dB at 9,750 50 dB at 14,750	1	PE87FL1002	$540.93	$513.88	$486.84	$465.20	28
12,200 - 12,700		50 dB at 11,450 50 dB at 13,450	2	PE87FL1004	$532.94	$506.29	$479.65	$458.33	29
14,000 - 14,800		50 dB at 12,850 50 dB at 15,950		PE87FL1005	$505.54	$480.26	$454.99	$434.76	30
17,200 - 18,200		35 dB at 16,200 35 dB at 19,200		PE87FL1008	$505.54	$480.26	$454.99	$434.76	31
17,200 - 21,200		50 dB at 13,450 50 dB at 24,950	1	PE87FL1007	$486.56	$462.23	$437.90	$418.44	32
17,300 - 18,100		50 dB at 16,200 50 dB at 19,200	2	PE87FL1006	$540.93	$513.88	$486.84	$465.20	33
17,700 - 21,200	VSAT	50 dB at 16,000 50 dB at 24,000		PE8743	$516.42	$490.60	$464.78	$444.12	34
18,200 - 19,200		35 dB at 17,200 35 dB at 20,200		PE87FL1009	$505.54	$480.26	$454.99	$434.76	35
19,200 - 20,200		35 dB at 18,200 35 dB at 21,200		PE87FL1010	$510.14	$484.63	$459.13	$438.72	36
20,200 - 21,200		35 dB at 19,200 35 dB at 22,200		PE87FL1011	$486.56	$462.23	$437.90	$418.44	37
27,500 - 31,000	VSAT	50 dB at 25,000 50 dB at 32,750	3	PE8747	$469.25	$445.79	$422.33	$403.56	38

Highpass Filters

Bandpass Frequency (MHz)	Application	Rejection (MHz)	Max. Insertion Loss (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
100 - 300		60 dB at 15	1	PE8717	$413.85	See Web for Volume Pricing			39
100 - 750		60 dB at 50		PE8716	$660.01				40
100 - 2,500		60 dB at 500		PE8715	$413.85				41
300 - 1,000		60 dB at 150		PE8718	$394.54				42
1,000 - 13,000		40 dB at 0	2	PE87FL1018	$848.67				43
2,000 - 18,000				PE87FL1019	$832.35				44

Lowpass Filters

Bandpass Frequency (MHz)	Application	Rejection (MHz)	Max. Insertion Loss (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
DC - 30		60 dB at 60	1	PE8723	$375.88	See Web for Volume Pricing			45
DC - 100		60 dB at 200		PE8719	$368.98				46
DC - 225		60 dB at 450		PE8722	$355.14				47
DC - 300		60 dB at 600		PE8724	$592.63				48
DC - 400		60 dB at 800		PE8726	$271.46				49
DC - 700		60 dB at 1,400		PE8727	$393.08				50
DC - 1,000		60 dB at 2,000		PE8720	$358.64				51
DC - 2,000		60 dB at 4,000		PE8721	$353.35				52
DC - 3,000		60 dB at 6,000		PE8725	$419.01				53
DC - 4,400		50 dB at 12,000	2	PE87FL1014	$475.84				54
DC - 7,000		50 dB at 15,000		PE87FL1015	$475.84				55
DC - 9,500		50 dB at 18,000		PE87FL1016	$475.84				56
DC - 11,000				PE87FL1017	$475.84				57

N

Band Pass

Bandpass Frequency (MHz)	Application	Rejection (MHz)	Max. Insertion Loss (dB)	Model No	1	2-4	5-9	10+	ROW
250 - 500				PE8729	$2,464.45	$2,378.19	$2,291.94	$2,218.01	58
500 - 1 GHz				PE8730	$2,648.30	$2,555.61	$2,462.92	$2,383.47	59
750 - 1.5 GHz				PE8731	$2,609.98	$2,518.63	$2,427.28	$2,348.98	60
1 GHz - 2 GHz				PE8732	$2,448.44	$2,362.74	$2,277.05	$2,203.60	61
1.5 GHz - 3 GHz				PE8733	$2,617.27	$2,525.67	$2,434.06	$2,355.54	62

Band Reject

Bandpass Frequency (MHz)	Application	Rejection (MHz)	Max. Insertion Loss (dB)	Model No	1	2-4	5-9	10+	ROW
100 - 200				PE8734	$2,679.26	$2,585.49	$2,491.71	$2,411.33	63
200 - 400				PE8735	$2,416.65	$2,332.07	$2,247.48	$2,174.99	64
250 - 500				PE8736	$2,857.88	$2,757.85	$2,657.83	$2,572.09	65
1 GHz - 2 GHz				PE8738	$2,583.56	$2,493.14	$2,402.71	$2,325.20	66

FREQUENCY DIVIDERS

Input Frequency (GHz)	Divide-By Prescaler	CW Input Power (CW) (dBm)	Typ Power Out (dBm)	Phase Noise @100 kHz (dBc/Hz)	DC Bias (Volts/mA)	Model No	1	2-4	5-9	10+	ROW
0.1 - 7	3	-12	-1	-150	+12 / 70	PE88D3000	$1,027.86	$966.19	$914.80	$873.68	67
	5				+12 / 80	PE88D25000	$974.68	$916.20	$867.47	$828.48	68
	15				+12 / 150	PE88D15000	$1,075.00	$1,010.50	$956.75	$913.75	69
0.1 - 12	8				+12 / 75	PE88D8003	$1,078.58	$1,013.87	$959.94	$916.79	70
	24		-1	-147	+12 / 140	PE88D24000	$1,247.00	$1,172.18	$1,109.83	$1,059.95	71
	40				+12 / 150	PE88D40000	$1,265.68	$1,189.74	$1,126.46	$1,075.83	72
0.1 - 12.5	10			-144	+12 / 200	PE88D1001	$1,315.04	$1,236.14	$1,170.39	$1,117.78	73
0.1 - 13	4		5	-151	+12 / 120	PE88D4003	$1,171.44	$1,101.15	$1,042.58	$995.72	74
	12			-145	+12 / 185	PE88D12000	$1,265.68	$1,189.74	$1,126.46	$1,075.83	75
	20		-1		+12 / 195	PE88D20000	$1,247.00	$1,172.18	$1,109.83	$1,059.95	76
0.1 - 15	5		5	-153	+5 / 205	PE88D5001	$1,640.28	$1,541.86	$1,459.85	$1,394.24	77
	6				+5 / 205	PE88D6000	$1,616.08	$1,519.12	$1,438.31	$1,373.67	78
	7				+5 / 205	PE88D7000	$1,616.08	$1,519.12	$1,438.31	$1,373.67	79
	9				+5 / 205	PE88D9000	$1,616.08	$1,519.12	$1,438.31	$1,373.67	80
0.1 - 20	2				+5 / 160	PE88D2002	$1,704.26	$1,602.00	$1,516.79	$1,448.62	81
	4				+5 / 170	PE88D4002	$1,640.28	$1,541.86	$1,459.85	$1,394.24	82
	8				+5 / 175	PE88D8002	$1,616.08	$1,519.12	$1,438.31	$1,373.67	83
0.2 - 6	10		-2	-144	+12 / 100	PE88D1002	$887.43	$834.18	$789.81	$754.32	84
	20		2		+12 / 95	PE88D20001	$887.43	$834.18	$789.81	$754.32	85
0.4 - 4	16				+12 / 70	PE88D16000	$774.00	$727.56	$688.86	$657.90	86
	32		1		+12 / 70	PE88D32000	$785.59	$738.45	$699.18	$667.75	87
0.5 - 8	5	-20	-1		+5 / 80	PE88D5000	$2,957.41	$2,839.11	$2,720.82	$2,602.52	88
0.5 - 18	2	-15	-4	-147	+12 / 85	PE88D2001	$1,479.93	$1,391.13	$1,317.14	$1,257.94	89
	4	-20			+5 / 93	PE88D4000	$4,217.06	$4,048.38	$3,879.70	$3,711.01	90
		-15		-147	+12 / 110	PE88D4001	$1,479.93	$1,391.13	$1,317.14	$1,257.94	91
	8				+12 / 110	PE88D8001	$1,560.67	$1,467.03	$1,389.00	$1,326.57	92
	10	-20	-1		+5 / 152	PE88D1000	$4,605.22	$4,328.91	$4,098.65	$3,914.44	93

MIXERS

Double Balanced

RF Range (GHz)	LO Range (GHz)	IF Range (GHz)	LO Power (dBm)	Conv. Loss (dB)	Connector	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
0.5 MHz- 500 MHz	0.5 MHz- 500 MHz	DC - 500 MHz	10	6.8	SMA	PE86X1013	$340.79		See Web for Volume Pricing		94
1 MHz- 2.7	1 MHz- 2.7	1 MHz - 2	10	7	SMA	PE86X1020	$434.79				95
			17			PE86X1021	$532.71				96
5 MHz- 1	5 MHz- 1	DC - 1	7	7	SMA	PE86X1014	$340.79				97
			13			PE86X1016	$323.15				98
5 MHz- 1.5	5 MHz- 1.5	DC - 1	7	7.5	SMA	PE86X1018	$340.79				99
5 MHz- 3.5	5 MHz- 3.5	5 MHz - 2.5	13	8	SMA	PE86X1022	$393.73				1
5 MHz- 4.2	5 MHz- 4.2	5 MHz - 3.5	13	9.8	SMA	PE86X1023	$434.79				2
10 MHz- 1	10 MHz- 1	DC - 800 MHz	4	7.2	SMA	PE86X1015	$340.79				3
10 MHz- 1.2	10 MHz- 1.2	DC - 1.2	13	8	SMA	PE86X1017	$341.73				4
40 MHz- 2.5	40 MHz- 2.5	DC - 1	13	8	SMA	PE86X1019	$473.96				5
800 MHz- 4.2	800 MHz- 4.2	DC - 800 MHz	13	9	SMA	PE86X1024	$379.95				6
2 - 8	2 - 8	DC - 1.5	10	5.5	SMA	PE8650	$739.96				7
2 - 18	2 - 18	DC - 600 MHz	10	6.5	SMA	PE8652	$959.44				8
2.25 - 18	2.25 - 18	DC - 3	13	11	SMA	PE86X1026	$1,214.26				9
2.5 - 6	2.5 - 6	DC - 1.5	17	8.7	SMA	PE86X1025	$493.54				10
3 - 10	3 - 10	DC - 4	17	9	SMA	PE86X1027	$1,214.26				11
5 - 18	5 - 18	DC - 4	10	6.2	SMA	PE8653	$1,054.98				12
5 - 20	5 - 20	DC - 3	20	10	SMA	PE86X1006	$1,481.05				13
						PE86X1008	$1,477.42				14
6 - 18	6 - 18	DC - 3	6	7.5	SMA	PE86X1007	$1,558.22				15
6 - 26	6 - 26	DC - 8	13	10	SMA	PE86X1028	$1,327.86				16
7 - 14	7 - 14	DC - 5	13		SMA	PE86X1003	$4,857.06				17
7 - 34	7 - 34	DC - 8	13	11	2.92mm	PE86X1029	$1,404.00				18
7 - 43	7 - 43	DC - 10	13	9	2.92mm	PE86X1009	$3,047.20				19
11 - 20	11 - 20	DC - 6	13		2.92mm	PE86X1004	$3,018.58				20
16 - 30	16 - 30	DC - 8	13	9	2.92mm	PE86X1030	$1,480.60				21
16 - 32	16 - 32	DC - 8	13		2.92mm	PE86X1000	$3,591.05				22
23 - 37	23 - 37	DC - 13	13	9	2.92mm	PE86X1002	$4,435.60				23
24 - 32	24 - 32	DC - 8	13	10.5	2.92mm	PE86X1031	$1,425.02				24
24 - 38	24 - 38	DC - 8	13	9	2.92mm	PE86X1001	$4,836.61				25
24 - 40	24 - 40	DC - 18	13	8	2.92mm	PE86X1010	$2,842.67				26

IQ

RF Range (GHz)	LO Range (GHz)	IF Range (GHz)	LO Power (dBm)	Conv. Loss (dB)	Connector	Model No	1	2-4	5-9	10+	ROW
4 - 8.5	4 - 8.5	DC - 3.5	15		SMA	PE86X9000	$3,287.88	$3,172.80	$3,057.73	$2,959.09	27

IQ

RF Range (GHz)	LO Range (GHz)	IF Range (GHz)	LO Power (dBm)	Conv. Loss (dB)	Connector	Model No	1	2-4	5-9	10+	ROW
6 - 10	6 - 10	DC - 3.5	19	7.5	SMA	PE86X9001	$3,287.88	$3,156.36	$3,024.85	$2,893.33	28
8.5 - 13.5	8.5 - 13.5	DC - 2	19	8	SMA	PE86X9002	$3,609.10	$3,464.74	$3,320.37	$3,176.01	29
11 - 16	11 - 16	DC - 3.5	19	9	SMA	PE86X9003	$3,944.71	$3,786.92	$3,629.13	$3,471.34	30
15 - 23	15 - 23	DC - 3.5	17	8	SMA	PE86X9004	$4,276.76	$4,105.69	$3,934.62	$3,763.55	31
20 - 31	20 - 31	DC - 4.5	17	10	2.92mm	PE86X9005	$5,433.85	$5,216.50	$4,999.14	$4,781.79	32
30 - 38	30 - 38	DC - 3.5	17	10.5	2.92mm	PE86X9006	$5,467.07	$5,248.39	$5,029.70	$4,811.02	33

Triple Balanced

RF Range (GHz)	LO Range (GHz)	IF Range (GHz)	LO Power (dBm)	Conv. Loss (dB)	Connector	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
2 - 18	2 - 18	1 - 6	13	8	SMA	PE86X1032	$2,195.96		See Web for Volume Pricing		34
6 - 18	6 - 18	1.5 - 8	10	7	SMA	PE8654	$1,054.98				35

MODULATOR

BiPhase

Freq. Band (GHz.)	Insertion Loss (dB)	Switching Speed (nsec)	Phase State (On/Off)	VSWR	RF Input Power (CW) (dBm)	Max Peak RF Input Power (1usec	RF Conn.	Model No	1	2-4	5-9	10+	ROW
0.5 MHz to 1	1.5	50	0º/180º	1.5:1	+20	0.5	SMA Female	PE86GM2000	$3,677.54	$3,548.83	$3,420.11	$3,309.79	36
1 to 2	3	30						PE86GM2001	$3,923.88	$3,786.54	$3,649.21	$3,531.49	37
2 to 4	2.5	75						PE86GM2002	$4,170.22	$4,024.26	$3,878.30	$3,753.20	38
2 to 6	1.7	50		1.6:1	+27			PE86GM2003	$4,416.56	$4,261.98	$4,107.40	$3,974.90	39
4 to 8	2.5	30		2.0:1	+20			PE86GM2004	$4,662.91	$4,499.71	$4,336.51	$4,196.62	40
6 to 12		15						PE86GM2005	$4,909.24	$4,737.42	$4,565.59	$4,418.32	41
8 to 18	3	75						PE86GM2006	$5,155.59	$4,975.14	$4,794.70	$4,640.03	42
2 to 18	3.5	35		1.9:1				PE86GM2007	$6,140.96	$5,926.03	$5,711.09	$5,526.86	43
26.5 to 40	5.5	50		2.0:1			2.92mm Female	PE86GM2008	$7,372.66	$7,114.62	$6,856.57	$6,635.39	44

FREQUENCY MULTIPLIERS

Active

Type	Input Freq. (GHz.)	Output Freq. (GHz.)	CW Input Power (dBm)	Fund. Iso. Typ (dB)	Conver-sion Gain (dB)	DC Voltage	Female In/Out Conn.	Model No	1	2-4	5-9	10+	ROW
Triplers	250 MHz - 350 MHz	750 MHz - 1.05	-3	40	7	12	SMA	PE88X2015	$695.18	$667.37	$639.57	$611.76	45
	320 MHz - 450 MHz	960 MHz - 1.35	-3	30	6			PE88X2016	$695.18	$667.37	$639.57	$611.76	46
	450 MHz - 600 MHz	1.35 - 1.8	-3	35	9			PE88X2017	$695.18	$667.37	$639.57	$611.76	47
	600 MHz - 750 MHz	1.8 - 2.25	-3	30	4			PE88X2018	$695.18	$667.37	$639.57	$611.76	48
	700 MHz - 1000 MHz	2.1 - 3	0	25	12			PE88X2019	$695.18	$667.37	$639.57	$611.76	49
	950 MHz - 1.5	2.85 - 4.5	0	20	9			PE88X2020	$695.18	$667.37	$639.57	$611.76	50
Doublers	4 - 10.5	8 - 21	6		8	5	SMA	PE88X2003*	$5,110.83	$4,906.40	$4,701.96	$4,497.53	51
	9 - 14.5	18 - 29	3	20	13		2.92mm	PE88X2000*	$4,919.16	$4,722.39	$4,525.63	$4,328.86	52
	12 - 16.5	24 - 33	3	20	14			PE88X2001*	$4,837.09	$4,643.61	$4,450.12	$4,256.64	53
	16 - 23	32 - 46	3	20	10			PE88X2002*	$5,397.13	$5,181.24	$4,965.36	$4,749.47	54

*Field Replaceable Connectors

Passive Doublers

Input Freq. (GHz.)	Output Freq. (GHz.)	Input Drive Power (dBm)	Conversion Loss (dB)	Fund. Iso. Typ (dB)	Female In/Out Conn.	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
10 MHz - 1000 MHz	20 MHz - 2	12	12	35	SMA	PE88X2010	$519.58		See Web for Volume Pricing		55
900 MHz - 1.8	1.8 - 4	12	14			PE88X2011	$519.58				56
1.25 - 3	2.5 - 6		15	25		PE88X2012	$519.58				57
1.5 - 5	3 - 10	13	8.5	25		PE8600	$746.50				58
2 - 4	4 - 8	12	14	25		PE88X2013	$519.58				59
2 - 6	4 - 12	13	11	25		PE8601	$785.69				60
4 - 8	8 - 16	12	17	25		PE88X2014	$519.58				61
4 - 9	8 - 18	13	10	25		PE8602	$795.01				62
9 - 13	18 - 26					PE8603	$795.09				63

*Field Replaceable Connectors

LIMITERS

High Rel

Frequency Range (GHz.)	Insertion Loss Max. (dB)	Input VSWR Typ.	Leakage Power Max. (dBm)	Recovery Time Typ. (ns)	Input Power (CW) Max. (W)	Peak Power Max. (W)	Limiting Threshold Typ. (dBm)	Model No	1	2-4	5-9	10+	ROW
20 MHz - 4	0.8	1.8:1	13	15,000	2	100	10	PE80L2003	$1,321.87	$1,269.00	$1,216.12	$1,163.25	64
500 MHz - 18	1.5	1.5:1	10	10	1			PE80L1000	$4,267.93	$4,097.21	$3,926.50	$3,755.78	65
	2	1.8:1	18	15,000	5		14	PE80L2005	$1,836.11	$1,762.67	$1,689.22	$1,615.78	66
2 - 8	1	2:1	13	40				PE80L1001	$5,067.97	$4,865.25	$4,662.53	$4,459.81	67
2 - 18	2	2:1	14	100	1	200	6	PE80L2001	$4,985.71	$4,786.28	$4,586.85	$4,387.42	68
	2.5	2:1		15,000	5	100		PE80L2006	$1,611.99	$1,547.51	$1,483.03	$1,418.55	69
	2	2:1		100	1	200		PE80L3000	$4,910.33	$4,713.92	$4,517.50	$4,321.09	70
6 - 18	2.5		15	12	10	100		PE80L2000	$3,844.13	$3,690.36	$3,536.60	$3,382.83	71
8 - 12	1.2	1.8:1	18	15,000	3		15	PE80L2004	$1,521.54	$1,460.68	$1,399.82	$1,338.96	72
12 - 18	1.5	1.5:1	10	10	1		1	PE80L4000	$5,271.43	$5,060.57	$4,849.72	$4,638.86	73
18 - 40	4	2.1:1	12	10		20	5	PE80L2002	$5,328.34	$5,115.21	$4,902.07	$4,688.94	74
	4.5	3:1	13	15,000		100	6	PE80L2007	$2,232.27	$2,142.98	$2,053.69	$1,964.40	75
26.5 - 40	3	2:1		15,000				PE80L2008	$1,899.19	$1,823.22	$1,747.25	$1,671.29	76

PIN-PIN

Frequency Range (GHz.)	Limiting Threshold Typ. (dBm)	Leakage @1W CW Input Max. (dBm)	Insertion Loss Max. (dBm)	Input VSWR Typ.	In Power (CW) Max. (W)	In Peak Power Max. (W)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
500 MHz - 1	12	20	0.4	1.4:1	1	100	PE8017	$508.43		See Web for Volume Pricing		77
500 MHz - 2		19	0.5	1.4:1			PE8018	$531.83				78
1 - 2	9	19	0.2	1.2:1			PE8019	$561.02				79
2 - 4	12	19	0.8	1.5:1			PE8020	$495.84				80
2 - 8	9	16	1.2	1.6:1			PE8021	$636.93				81
2 - 18	12	18	2.5	2.2:1			PE8022	$642.23				82
4 - 8	9	16	1	1.3:1			PE8023	$594.70				83
6 - 18	12	16	2.2	2:1			PE8024	$619.55				84
7 - 12		16	1.8	1.8:1			PE8025	$591.50				85
8 - 16		16	2	2:1			PE8026	$563.33				86
11 - 18	9	16		2:1			PE8027	$676.04				87

PIN-Schottky

Frequency Range (GHz.)	Limiting Threshold Typ. (dBm)	Leakage @1W CW Input Max. (dBm)	Insertion Loss Max. (dBm)	Input VSWR Typ.	In Power (CW) Max. (W)	In Peak Power Max. (W)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
500 MHz - 1	12	14	0.5	1.4:1	1	100	PE8028	$489.35		See Web for Volume Pricing		88
500 MHz - 2	9	14	0.4	1.25:1		200	PE8029	$540.84				89
1 - 2	4	14	0.6	1.4:1		100	PE8030	$663.84				90
2 - 4		14	0.8	1.5:1		200	PE8031	$623.43				91
2 - 8	9	14	1.2	1.4:1			PE8032	$565.55				92
2 - 18	4	18	2.5	2.2:1		100	PE8033	$630.33				93
4 - 8		13	1.4	1.5:1			PE8034	$646.51				94
6 - 18		13	2.5	2.2:1			PE8035	$343.64				95
7 - 12		16	1.6	1.6:1			PE8036	$625.36				96
8 - 16	9	12	2	1.5:1		200	PE8037	$779.28				97

DETECTORS

Biased Detectors

Frequency Range (GHz.)	Polarity	Voltage Sensitivity (mV/mW)	Flatness (dB)	Input Power (dBm)	TSS (dBm)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
500 MHz - 1	Negative	1,800	0.25	23	-54	PE8001	$681.57		See Web for Volume Pricing		1
	Positive		0.5			PE8001-P	$672.29				2
1 - 2	Negative	2,000	0.25		-52	PE8002	$516.04				3
	Positive					PE8002-P	$846.07				4
2 - 4	Negative		0.5			PE8003	$812.18				5
	Positive					PE8003-P	$752.06				6
4 - 8	Negative					PE8044	$582.66				7
	Positive					PE8004-P	$577.25				8
6 - 18	Negative	1,600	0.8			PE8005	$724.44				9
	Positive					PE8005-P	$634.97				10
8 - 12	Negative	1,800	0.5			PE8006	$786.60				11
	Positive					PE8006-P	$751.03				12
8 - 16	Negative		0.6			PE8007	$549.06				13
	Positive					PE8007-P	$714.72				14
8 - 18	Negative	1,600	0.7			PE8008	$663.84				15
	Positive					PE8008-P	$666.72				16
18 - 26	Negative	1,500	1			PE8009	$625.96				17
	Positive					PE8009-P	$806.78				18

Finline Detectors

Frequency Range (GHz.)	Output Polarity	Input Power (dBm)	Video Output Typ. (V)	Voltage Sensitivity (mV/mW)	Model No	1	2-4	5-9	10+	ROW
100 MHz - 12.4		27		800	PE80T1004	$1,135.19	$1,089.78	$1,044.37	$998.97	19
100 MHz - 18					PE80T1005	$1,348.82	$1,294.87	$1,240.91	$1,186.96	20

Log Detectors

Frequency Range (GHz.)	Imp. (Ohm)	Slope (mV/dB)	Input Power Max. (dBm)	Output Voltage Max. (dB)	Slew Rate (V/us)	Model No	1-4	5-9	10-24	25+	ROW
10 MHz - 3	50	40	10	2	1	PE8040	$585.03	$555.78	$526.53	$503.13	21

Phase Detectors

Frequency Range (GHz.)	Input Power Max. (dBm)	VSWR Max.	DC Voltage	Model No	1	2-4	5-9	10+	ROW
3 MHz - 300 MHz	17	17	15	PE80T4000	$1,389.43	$1,333.85	$1,278.28	$1,222.70	22
5 MHz - 25 MHz				PE80T4002	$1,161.10	$1,114.66	$1,068.21	$1,021.77	23
200 MHz - 800 MHz	10	10		PE80T4001	$1,542.78	$1,481.07	$1,419.36	$1,357.65	24

Power Detectors

Frequency Range (GHz.)	Dynamic Range (dB)	True RMS Output Voltage Typ (V)	Output Slope	VSWR	Max RF Input Power (dBm)	RF Connectors	Model No	1	2-4	5-9	10+	ROW
30 MHz - 4	80	0.62 - 1.89	Positive	1.5:1	20	SMA Female	PE80P1001	$760.01	$714.41	$676.41	$646.01	25
50 MHz - 3	60	0.12 - 2.1		1.3:1	10		PE80P1002	$712.13	$669.40	$633.80	$605.31	26
50 MHz - 5	30	0.15 - 4.95		1.4:1	15		PE80P1000	$712.13	$669.40	$633.80	$605.31	27

Schottky Zero Bias Detectors

Frequency Range (GHz.)	Imp. (Ohm)	Polarity	Voltage Sensitivity (mV/mW)	VSWR Max	Video Capacitance (pF)	Signal Level & Level Min Input (dBm)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
10 MHz - 2	50	Negative	500	1.2:1	470	-30	PE8010	$652.27		See Web for Volume Pricing		28
10 MHz - 12.4				1.6:1			PE8012	$569.22				29
		Positive					PE8012P	$586.73				30
10 MHz - 18		Negative		1.7:1			PE80T1003	$905.61				31
10 MHz - 18.5			450				PE8013	$691.55				32
10 MHz - 26.5			100				PE8014	$754.28				33
2 - 4			500	1.45:1	20		PE8015	$654.87				34
2 - 8				1.5:1			PE8016	$663.84				35

Threshold Detectors

Frequency Range (GHz.)	Imp. (Ohm)	Signal Level & Input Level Min. (dBm)	Input Power Max. (dBm)	Propagation Delay Typ. (ns)	DC Voltage	Model No	1	2-4	5-9	10+	ROW
2 - 18	50	-20	10	15	15	PE80T1000	$4,626.32	$4,441.27	$4,256.21	$4,071.16	36
		-45		20	12	PE80T1001	$7,560.21	$7,257.80	$6,955.39	$6,652.98	37
16 - 40		-20	17		15	PE80T1002	$5,897.15	$5,661.26	$5,425.38	$5,189.49	38

Tunnel Diode Zero Bias Detectors

Frequency Range (GHz.)	Output Polarity	VSWR Max	Pulse Video Response Risetime Typ. (ns)	Voltage Sensitivity Typ. (mV/mW)	Flatness Max. (dB)	Input Power Max. (dBm)	Video Capacitance Typ. (pF)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
100 MHz - 2	Negative	2:1	5	800	0.75	17	470	PE80T6000	$508.16		See Web for Volume Pricing		39
	Positive					17		PE80T6001	$508.16				40
100 MHz - 4	Negative	2.2:1				17		PE80T6002	$530.40				41
	Positive					17		PE80T6003	$530.40				42
500 MHz - 1	Negative	2:1		1,000	0.5	17	100	PE80T6010	$398.67				43
	Positive					17		PE80T6011	$398.67				44
500 MHz - 18	Negative	3.5:1		400	1	17		PE80T6004	$1,227.98				45
	Positive					17		PE80T6005	$1,227.98				46
1 - 2	Negative	2:1		1,000	0.5	17	50	PE80T6012	$495.74				47
	Positive					17		PE80T6013	$495.74				48
2 - 4	Negative					17	20	PE80T6014	$517.24				49
	Positive					17		PE80T6015	$509.60				50

Tunnel Diode Zero Bias Detectors

Frequency Range (GHz.)	Output Polarity	VSWR Max	Pulse Video Response Risetime Typ. (ns)	Voltage Sensitivity Typ. (mV/mW)	Flatness Max. (dB)	Input Power Max. (dBm)	Video Capacitance Typ. (pF)	Model No	1-4	5-9	10-24	25+	ROW
2 - 6	Negative	2.5:1	5	1,000	0.5	17	20	PE80T6016	$527.79	$501.40	$475.01	$453.90	51
	Positive					17		PE80T6017	$527.79	$501.40	$475.01	$453.90	52
2 - 18	Negative	3.5:1		500	1	17		PE80T6006	$743.52	$706.34	$669.17	$639.43	53
	Positive					17		PE80T6007	$742.14	$705.03	$667.93	$638.24	54
4 - 8	Negative	2.5:1		900	0.7	17		PE80T6018	$559.35	$531.38	$503.42	$481.04	55
	Positive					17		PE80T6019	$559.35	$531.38	$503.42	$481.04	56
6 - 12	Negative	2.7:1		800	0.6	17	10	PE80T6020	$613.60	$582.92	$552.24	$527.70	57
	Positive					17		PE80T6021	$647.08	$614.73	$582.37	$556.49	58
6 - 18	Negative	3:1		700	0.75	17		PE80T6008	$682.94	$648.79	$614.65	$587.33	59
	Positive					17		PE80T6009	$720.20	$684.19	$648.18	$619.37	60
12 - 18	Negative				0.7	17		PE80T6022	$721.31	$685.24	$649.18	$620.33	61
	Positive					17		PE80T6023	$749.44	$711.97	$674.50	$644.52	62
18 - 26	Negative	4:1		400	1	17	5	PE80T6024	$837.42	$795.55	$753.68	$720.18	63
	Positive					17		PE80T6025	$837.42	$795.55	$753.68	$720.18	64

NOISE SOURCES

Frequency Range (MHz.)	Design	Noise Output (ENR dB)	Connector	Model No	1	2-4	5-9	10+	ROW
0.01 - 2,000	Calibrated	30	SMA Female	PE85N1001	$2,750.14	$2,640.13	$2,530.13	$2,420.12	65
		15		PE85N1019	$2,613.61	$2,509.07	$2,404.52	$2,299.98	66
		30		PE85N1020	$2,646.91	$2,541.03	$2,435.16	$2,329.28	67
		15		PE85N1000	$2,711.12	$2,602.68	$2,494.23	$2,385.79	68
0.1 - 500	Calibrated, Amplified			PE85N1010	$3,635.69	$3,490.26	$3,344.83	$3,199.41	69
0.2 - 500	SMT Pin Packaged	31	SMT Pin Packaged	PE85NS4000	$189.22	$181.65	$174.08	$166.51	70
0.2 - 2,000				PE85NS4001	$207.41	$199.11	$190.82	$182.52	71
				PE85NS4003	$298.39	$286.45	$274.52	$262.58	72
0.2 - 3,000		51		PE85NS4002	$225.61	$216.59	$207.56	$198.54	73
				PE85NS4004	$371.16	$356.31	$341.47	$326.62	74
1 - 2,000	Calibrated, Amplified, Bench Top		SMA Female	PE85N1017	$17,905.13	$17,188.92	$16,472.72	$15,756.51	75
10 - 2,000	Calibrated, Amplified			PE85N1011	$3,549.82	$3,407.83	$3,265.83	$3,123.84	76
	DIP Packaged		DIP Packaged	PE85NS5000	$1,146.21	$1,100.36	$1,054.51	$1,008.66	77
				PE85NS5002	$1,218.99	$1,170.23	$1,121.47	$1,072.71	78
10 - 3,000	Calibrated, Amplified		SMA Female	PE85N1012	$4,166.66	$3,999.99	$3,833.33	$3,666.66	79
	Calibrated, Amplified, Bench Top			PE85N1018	$19,605.61	$18,821.39	$18,037.16	$17,252.94	80
	DIP Packaged		DIP Packaged	PE85NS5001	$1,510.09	$1,449.69	$1,389.28	$1,328.88	81
				PE85NS5003	$1,582.86	$1,519.55	$1,456.23	$1,392.92	82
10 - 6,000	Calibrated	15	SMA Female	PE85N1002	$3,276.77	$3,145.70	$3,014.63	$2,883.56	83
		26		PE85N1003	$3,706.26	$3,558.01	$3,409.76	$3,261.51	84
		15		PE85N1021	$3,276.77	$3,145.70	$3,014.63	$2,883.56	85
	Calibrated, Amplified			PE85N1013	$5,357.19	$5,142.90	$4,928.61	$4,714.33	86
10 - 18,000	Calibrated	14	SMA Male	PE85N1006	$4,076.45	$3,913.39	$3,750.33	$3,587.28	87
10 - 26,000		13	3.5mm Male	PE85N1007	$5,636.36	$5,410.91	$5,185.45	$4,960.00	88
100 - 40,000		10	2.92mm Male	PE85N1008	$9,011.08	$8,650.64	$8,290.19	$7,929.75	89
100 - 60,000		7	1.85mm Male	PE85N1009	$18,865.41	$18,110.79	$17,356.18	$16,601.56	90
1,000 - 2,000		30	SMA Male	PE8505	$1,502.65	$1,442.54	$1,382.44	$1,322.33	91
1,000 - 18,000		15	SMA Female	PE85N1022	$3,736.47	$3,587.01	$3,437.55	$3,288.09	92
				PE85N1004	$3,940.31	$3,782.70	$3,625.09	$3,467.47	93
		23		PE85N1005	$4,095.95	$3,932.11	$3,768.27	$3,604.44	94
2,000 - 4,000		15.5	SMA Male	PE8501	$1,847.68	$1,773.77	$1,699.87	$1,625.96	95
		30		PE8506	$1,901.79	$1,825.72	$1,749.65	$1,673.58	96
3,700 - 4,200	Calibrated, Integral Isolator		SMA Female	PE85N1014	$3,736.47	$3,587.01	$3,437.55	$3,288.09	97
4,000 - 8,000	Calibrated		SMA Male	PE8507	$1,851.08	$1,777.04	$1,702.99	$1,628.95	98

Frequency Range (MHz.)	Design	Noise Output (ENR dB)	Connector	Model No	1	2-4	5-9	10+	ROW
7,200 - 8,400	Calibrated, Integral Isolator		SMA Female	PE85N1015	$3,865.56	$3,710.94	$3,556.32	$3,401.69	99
8,000 - 12,000	Calibrated	15.5	SMA Male	PE8503	$1,937.84	$1,860.33	$1,782.81	$1,705.30	1
				PE8508	$2,145.32	$2,059.51	$1,973.69	$1,887.88	2
10,700 - 12,700	Calibrated, Integral Isolator		SMA Female	PE85N1016	$4,383.44	$4,208.10	$4,032.76	$3,857.43	3
12,000 - 18,000	Calibrated	15.5	SMA Male	PE8504	$2,269.45	$2,178.67	$2,087.89	$1,997.12	4
				PE8509	$1,894.77	$1,818.98	$1,743.19	$1,667.40	5
26,500 - 40,000			BNC Female	PEWNS2000	$10,916.25	$10,479.60	$10,042.95	$9,606.30	6
33,000 - 50,000				PEWNS2001	$14,035.18	$13,473.77	$12,912.37	$12,350.96	7
40,000 - 60,000				PEWNS2002	$17,154.12	$16,467.96	$15,781.79	$15,095.63	8
50,000 - 75,000				PEWNS2003	$20,273.05	$19,462.13	$18,651.21	$17,840.28	9

PHASE SHIFTERS AND TRIMMERS

Adjustable Phase Trimmers

Connector	Gender	Frequency Range (MHz.)	Deg. Phase Adjustment per GHz	Max. Insertion Loss (dB)	Model No	1-9	10-24	25-49	50+	ROW
SMA	Male	DC - 18,000	10	3.4	PE8203	$207.23	$196.87	$186.51	$178.22	10

8 Bit Programmable Phase Shifter

Connector	Gender	Frequency Range (MHz.)	Deg. Phase Adjustment per GHz	Max. Insertion Loss (dB)	Model No	1	2-4	5-9	10+	ROW
2.92mm	Female	32,000 - 37,000			PE82P5003	$15,282.14	$14,670.85	$14,059.57	$13,448.28	11
SMA	Female	500 - 2,000		13	PE82P5000	$9,343.03	$8,969.31	$8,595.59	$8,221.87	12
		6,000 - 18,000		12	PE82P5002	$16,064.89	$15,422.29	$14,779.70	$14,137.10	13

Adjustable Phase Shifter



Connector	Gender	Frequency Range (MHz.)	Deg. Phase Adjustment per GHz	Max. Insertion Loss (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
2.92mm	Female	18,000 - 40,000		2.5	PE82P1000	$3,056.00				14
SMA	Female	DC - 2,300		0.5	PE8243	$1,073.93		See Web for Volume Pricing		15
		DC - 4,300			PE8244	$1,165.94				16
		DC - 8,200		0.6	PE8245	$1,130.20				17
		DC - 12,700		0.7	PE8246	$1,266.36				18
		DC - 18,000		1	PE8247	$1,272.69				19
					PE8255	$1,746.88				20
		18,000 - 26,500		1.5	PE8253	$1,396.16				21

Analog Phase Shifter

Connector	Gender	Frequency Range (MHz.)	Deg. Phase Adjustment per GHz	Max. Insertion Loss (dB)	Model No	1	2-4	5-9	10+	ROW
SMA	Female	5,000 - 18,000	40	12	PE82P2000	$6,482.18	$6,222.89	$5,963.61	$5,704.32	22
		6,000 - 15,000	120	10	PE82P2001	$5,991.26	$5,751.61	$5,511.96	$5,272.31	23

POWER DIVIDERS

50 Ohm

Ports	Freq. Range (MHz.)	Connector	Gender	Maximum Power	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
2 WAY	0-67,000	1.85mm	Female	0.5 Watt	PE20DV1057	$3,532.26	See Web for Volume Pricing	24
	350-6,000	SMA		30 Watt	PE20DV1053	$299.50		25
	2,000-18,000	N			PE20DV1049	$670.12		26
		SMA			PE20DV1044	$359.40		27
	4,000-8,000				PE20DV1045	$140.17		28
	10,000-65,000	1.85mm		10 Watt	PE20DV1073	$2,618.82		29
4 WAY	375-6,000	N		30 Watt	PE20DV1050	$471.71		30
	1,000-4,000				PE20DV1051	$326.61		31
	2,000-4,000	SMA			PE20DV1046	$209.66		32
	4,000-8,000				PE20DV1047	$218.22		33
	6,000-18,000				PE20DV1048	$479.20		34
8 WAY	5-500	N		10 Watt	PE20DV1052	$627.29		35

Reactive

Ports	Freq. Range (MHz.)	Connector	Gender	Maximum Power	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
2 WAY	2-500	BNC	Female	1 Watt	PE2000	$260.84	See Web for Volume Pricing	36
		N			PE2044	$566.29		37
		SMA			PE2070	$553.04		38
	10-1,000	N			PE2047	$560.44		39
	376-2,500	7/16 DIN		300 Watt	PE20DV1041	$211.44		40
	500-1,000	N		10 Watt	PE2032	$654.82		41
		SMA		30 Watt	PE20DV019	$131.73		42
	500-2,000			20 Watt	PE20DV009	$235.33		43
	698-2,700			10 Watt	PE20DV007	$129.03		44
	800-2,400			20 Watt	PE20DV008	$119.99		45
	1,000-2,000			30 Watt	PE20DV014	$131.73		46
	1,000-4,000			20 Watt	PE20DV013	$235.33		47
	2,000-4,000			30 Watt	PE20DV016	$131.73		48
	2,000-8,000				PE20DV000	$290.13		49
	2,000-18,000			20 Watt	PE20DV005	$409.43		50
				30 Watt	PE2028	$634.23		51
	7,000-12,400		Male	10 Watt	PE2081	$425.26		52
	8,000-12,400	N	Female		PE2036	$736.65		53
	10,000-40,000	2.92mm			PE2078	$2,127.32		54
				12 Watt	PE2077	$1,886.44		55
	10,000-50,000	2.4mm		10 Watt	PE2079A	$2,340.31		56
	12,000-18,000	N			PE2037	$1,041.36		57
3 WAY	376-2,200			500 Watt	PE20DV1040	$289.43		58
	2,000-4,000	SMA		30 Watt	PE20DV017	$215.99		59
	2,000-8,000				PE20DV001	$363.06		60

Reactive



Ports	Freq. Range (MHz.)	Connector	Gender	Maximum Power	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
4 WAY	2-500	BNC	Female	1 Watt	PE2001	$466.91	See Web for Volume Pricing			61
	10-1,000				PE2004	$744.17				62
	500-1,000	N		10 Watt	PE2038	$1,036.35				63
		SMA		30 Watt	PE20DV020	$209.35				64
	500-2,000				PE20DV010	$251.49				65
	800-2,500			20 Watt	PE20DV012	$149.39				66
	1,000-2,000	N		10 Watt	PE2039	$1,083.18				67
		SMA		30 Watt	PE20DV015	$209.35				68
	2,000-4,000	N			PE2040	$1,039.74				69
		SMA			PE20DV018	$201.50				70
	2,000-8,000				PE20DV002	$368.68				71
	2,000-18,000				PE20DV006	$864.51				72
6 WAY	1-175	BNC		1 Watt	PE2006	$665.52				73
	2,000-8,000	SMA		30 Watt	PE20DV003	$496.86				74
8 WAY	500-2,000				PE20DV011	$310.67				75
	2,000-8,000				PE20DV004	$683.98				76
12 WAY	2-500	BNC		1 Watt	PE2005	$894.99				77

Resistive

Ports	Freq. Range (MHz.)	Connector	Gender	Maximum Power	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
2 WAY	0-6,000	SMA	Male	2 Watt	PE2082	$335.55	See Web for Volume Pricing			78
	0-12,400	2.92mm		1 Watt	PE2063	$514.26				79
		SMA			PE2067	$496.42				80
	0-18,000	2.92mm			PE2064	$595.90				81
		N			PE2066	$554.40				82
		SMA	Female		PE2084	$368.04				83
			Male		PE2068	$544.82				84
	0-26,500	2.92mm	Female		PE2083	$750.05				85
			Male		PE2065	$784.16				86
	0-50,000	2.4mm	Female	0.5 Watt	PE20DV1056	$2,020.46				87

Wilkinson

Ports	Freq. Range (MHz.)	Connector	Gender	Maximum Power	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
2 WAY	10-1,000	BNC	Female	1 Watt	PE2003	$493.05	See Web for Volume Pricing			88
	500-1,000	SMA		10 Watt	PE2008	$411.17				89
	500-2,000			30 Watt	PE20S0022	$442.24				90
	617-2,700	4.1/9.5 Mini DIN			PE20DV1033A	$314.42				91
		N			PE20DV1032A	$276.40				92
	690-2,700			10 Watt	PE2092	$146.88				93
		SMA			PE2088	$125.42				94
	800-2,500	N		50 Watt	PE20S0025	$474.68				95
		SMA		10 Watt	PE2074	$298.34				96
	1,000-2,000	N		50 Watt	PE2033	$681.02				97
		SMA		10 Watt	PE2011	$377.65				98
	1,000-26,500	2.92mm		20 Watt	PE20DV1058	$1,009.68				99
	1,000-40,000				PE20DV1059	$1,620.34				1
	2,000-4,000	N		10 Watt	PE2034	$607.07				2
		SMA			PE2014	$317.40				3
	2,000-8,000				PE2026	$431.94				4
	2,000-40,000	2.92mm		20 Watt	PE20DV1060	$1,346.60				5

Wilkinson

Ports	Freq. Range (MHz.)	Connector	Gender	Maximum Power	Model No	1 Pc. Price		See Web for Volume Pricing		ROW
2 WAY	4,000-8,000	N	Female	30 Watt	PE2035	$712.78		See Web for Volume Pricing		6
		SMA	Male	10 Watt	PE2080	$436.56				7
	6,000-40,000	2.92mm	Female	20 Watt	PE20DV1061	$1,234.30				8
	7,000-12,400	SMA		10 Watt	PE2020	$417.44				9
	8,000-18,000				PE2027	$717.36				10
	10,000-43,300	2.92mm		20 Watt	PE20DV1062	$1,121.98				11
	12,000-18,000	SMA		10 Watt	PE2023	$456.66				12
	15,000-26,500			20 Watt	PE20DV1063	$672.74				13
	18,000-40,000	2.92mm			PE20DV1064	$1,187.97				14
	26,500-40,000				PE20DV1065	$897.36				15
3 WAY	690-2,700	N		10 Watt	PE2093	$235.95				16
		SMA			PE2090	$222.58				17
	698-2,700	N		30 Watt	PE20DV1034A	$319.88				18
	800-2,500			50 Watt	PE20S0019	$530.12				19
4 WAY	500-1,000	SMA		30 Watt	PE2009	$546.03				20
	500-2,000				PE20S0024	$526.11				21
	690-2,700	N		10 Watt	PE2094	$276.13				22
		SMA			PE2089	$245.30				23
	698-2,700	N		30 Watt	PE20DV1036A	$506.65				24
	800-2,500	SMA			PE20S0020	$446.63				25
	1,000-2,000			10 Watt	PE2012	$561.56				26
	2,000-8,000			30 Watt	PE2031	$645.78				27
	2,000-18,000			10 Watt	PE2029	$1,204.55				28
	2,000-26,500			20 Watt	PE20DV1067	$1,121.98				29
	4,000-8,000	N		10 Watt	PE2041	$931.64				30
	6,000-40,000	2.92mm		20 Watt	PE20DV1068	$1,458.92				31
	7,000-12,400	SMA		10 Watt	PE2021	$561.77				32
	18,000-40,000	2.92mm		20 Watt	PE20DV1069	$1,346.60				33
8 WAY	500-2,000	SMA		30 Watt	PE20S0023	$613.59				34
	690-2,700	N		10 Watt	PE2095	$453.58				35
		SMA			PE2091	$310.74				36
	698-2,700	4.1/9.5 Mini DIN		30 Watt	PE20DV1039A	$869.29				37
		N			PE20DV1038A	$741.18				38
	800-2,500	SMA			PE20S0021	$701.98				39

75 Ohm

Reactive

Ports	Freq. Range (MHz.)	Connector	Gender	Maximum Power	Model No	1 Pc. Price		See Web for Volume Pricing		ROW
2 WAY	2-500	BNC	Female	1 Watt	PE2048	$528.95		See Web for Volume Pricing		40
	10-1,000				PE2062	$261.60				41
4 WAY	2-500				PE2049	$474.62				42
8 WAY					PE2061	$783.79				43

RF COMBINERS

Broadband

Frequency Range (GHz)	Ports	Connector 1	Connector 2	Power Rating	Isolation (dB)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
20 MHz - 1	2	N Female	N Female	500 W	10	PE20S0004	$2,539.19	See Web for Volume Pricing			44
		SMA Female	SMA Female	100 W	15	PE20S0001	$1,272.16				45
	4	N Female	N Female	300 W	12	PE20S0003	$2,643.43				46
		SMA Female	SMA Female	200 W		PE20S0002	$1,786.72				47
80 MHz - 1		N Female	N Female	500 W		PE20S0006	$2,653.59				48
		SMA Female	SMA Female	200 W	-12	PE20S0005	$1,786.72				49
500 MHz - 2.5	2		N Female		13	PE20S0007	$1,837.63				50
800 MHz - 2.5		N Female		600 W	8	PE20S0011	$2,388.24				51
			SC Female	800 W		PE20S0010	$2,459.00				52
800 MHz - 4.2		SMA Female	N Female	200 W	10	PE20S0012	$2,420.41				53
800 MHz - 2.5	4	N Female		600 W	6	PE20S0009	$2,564.17				54
800 MHz - 4.2		SMA Female		200 W	8	PE20S0013	$2,379.01				55
800 MHz - 2.5			SMA Female		12	PE20S0008	$2,103.00				56
1 - 6				100 W	6	PE20S0014	$1,992.08				57
2 - 6	2				12	PE20S0015	$844.54				58
	4	N Female	N Female	400 W		PE20S0017	$2,667.62				59
		SMA Female	SMA Female	100 W	10	PE20S0016	$1,085.59				60

ROTARY JOINTS

Connector A	Connector B	Max. Frequency (MHz.)	Input Power	VSWR	Model No	1-9	10-24	25-49	50+	ROW
SMA	PCB	DC - 6,000	30 WATT	1.15:1	PE1401	$158.08	$150.18	$142.27	$135.95	61
2.92mm	2.92mm	DC - 18,000		1.4:1	PE1400	$189.70	$180.22	$170.73	$163.14	62
					PE1402	$174.44	$167.46	$162.23	$158.74	63
SMA	SMA				PE1406	$285.01	Call	Call	Call	64

SURGE PROTECTORS

In-Line Surge Protectors

Impedance	Connector	Gender	Frequency Range (MHz.)	Mount Type	Maximum Power	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
50 Ohm	4.3-10	Female to Female	698 - 2,700	Bulkhead	500 Watt	PE73SP1051	$158.39	See Web for Volume Pricing			65
						PE73SP1061	$190.49				66
		Female to Male				PE73SP1062	$193.35				67
		Male to Female	555 - 4,000		200 Watt	PE73SP1070	$136.54				68
			698 - 2,700	Bulkhead	500 Watt	PE73SP1060	$158.39				69
50 Ohm	7/16 DIN	Female to Female	100 - 512	None	750 Watt	PE73SP1037	$175.97				70
			698 - 2,700	Bulkhead	1000 Watt	PE73SP1004	$154.59				71
			800 - 2,250		Watt	PE73SP1063	$117.74				72
		Female to Male	698 - 2,160	Bulkhead	500 Watt	PE73SP1008	$163.84				73
			698 - 2,700		1000 Watt	PE73SP1005	$154.59				74
					500 Watt	PE73SP1006	$153.98				75
						PE73SP1007	$163.84				76
		Male to Female	100 - 512	None	750 Watt	PE73SP1034	$173.37				77
			800 - 2,250		Watt	PE73SP1064	$117.74				78
			800 - 2,500	None	300 Watt	PE73SP1017	$157.71				79
50 Ohm	N	Female to Female	DC - 2,400	Bulkhead	50 Watt	PE73SP1040	$87.52				80
			DC - 2,500		2000 Watt	PE7301-4	$197.11				81

In-Line Surge Protectors

Impedance	Connector	Gender	Frequency Range (MHz.)	Mount Type	Maximum Power	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
50 Ohm	N	Female to Female	DC - 3,000	Bulkhead	200 Watt	PE7301-3	$189.69	See Web for Volume Pricing			82
					40 Watt	PE73SP1039	$68.03				83
				None	200 Watt	PE7301-1	$175.88				84
					2000 Watt	PE7301-2	$182.89				85
			DC - 7,000	Bulkhead	90 Watt	PE73SP1038	$52.03				86
			1.5 - 700		500 Watt	PE73SP1027	$119.72				87
					3000 Watt	PE73SP1030	$89.16				88
				None	2000 Watt	PE73SP1025	$73.71				89
			10 - 1,000	Bulkhead	1500 Watt	PE73SP1024	$81.28				90
			40 - 400	None	100 Watt	PE73SP1015	$168.76				91
						PE73SP1018	$168.76				92
			100 - 512		750 Watt	PE73SP1033	$123.18				93
						PE73SP1035	$123.18				94
			125 - 1,000	Bulkhead	500 Watt	PE73SP1022	$89.16				95
					200 Watt	PE73SP1029	$119.72				96
					375 Watt	PE73SP1021	$73.71				97
			400 - 1,200		300 Watt	PE73SP1019	$145.64				98
			698 - 2,700	Bulkhead	500 Watt	PE73SP1000	$110.42				99
			800 - 2,250		Watt	PE73SP1065	$100.70				1
			800 - 2,500	None	300 Watt	PE73SP1010	$147.82				2
						PE73SP1013	$147.82				3
						PE73SP1014	$147.82				4
			1,800 - 6,000	Bulkhead	10 Watt	PE73SP1050	$112.49				5
			2,000 - 6,000			PE73SP1048	$64.26				6
		Female to Male	DC - 2,400		50 Watt	PE73SP1042	$87.52				7
			DC - 7,000		90 Watt	PE73SP1041	$52.03				8
			698 - 2,700		500 Watt	PE73SP1001	$110.42				9
						PE73SP1002	$122.04				10
						PE73SP1003	$126.95				11
			2,000 - 6,000		10 Watt	PE73SP1049	$64.26				12
		Male to Female	10 - 1,000		1500 Watt	PE73SP1028	$81.28				13
			100 - 512	None	750 Watt	PE73SP1036	$121.36				14
			125 - 1,000	Bulkhead	500 Watt	PE73SP1031	$89.16				15
				None	375 Watt	PE73SP1023	$73.71				16
			800 - 2,250		Watt	PE73SP1066	$100.70				17
			800 - 2,500	None	300 Watt	PE73SP1011	$147.82				18
	SMA	Female to Female	DC - 5,800	Bulkhead	200 Watt	PE73SP1068	$46.53				19
		Female to Male				PE73SP1067	$46.53				20
						PE73SP1069	$46.53				21
	TNC	Female to Female	800 - 2,500	None	300 Watt	PE73SP1016	$147.82				22
	UHF	Female to Female	1.5 - 700	Bulkhead	2000 Watt	PE73SP1032	$86.12				23
						PE73SP1026	$78.47				24

Surge Protector Replacement Cartridges

Cartridge For	Maximum Power	Model No	1-24	25-49	50-99	100+	ROW
PE7301	200 Watt	PE7301-200CART	$35.11	$33.35	$31.60	$30.19	25
	2,000 Watt	PE7301-2000CART	$31.60	$30.02	$28.44	$27.18	26
PE7139 & PE7140	1,500 Watt	PE7139-CART	$21.60	$20.74	$20.09	$19.66	27

INDEX GUIDE TO
SWITCHES

SWITCHES 324

ELECTROMECHANICAL RELAY SWITCHES 324

- 1M Life Cycles 324
- 2M Life Cycles 326
- 2.5M Life Cycles 328
- 5M Life Cycles 328
- 10M Life Cycles 329
- Special Applications 330

GaN HIGH POWER SWITCHES 335

HIGH ISOLATION SWITCHES 335

HIGH ISOLATION USB SWITCHES 335

MANUAL SWITCHES 331

PIN DIODE SWITCHES 331

- SPST 331
- SPDT 332
- SP3T 333
- SP4T 333
- SP5T 334
- SP6T 334
- SP8T 334
- SP12T 334
- Transfer 334

SMT PACKAGED ELECTROMECHANICAL SWITCHES 330

Electromechanical Relay Switches

1M Life Cycles

Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: Non-Terminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
8 GHz	SP6T	TNC Female	NO/Non-T	70	0.6	12	50	PE71S6206	$1,960.27		See Web for Volume Pricing		1
				60		28		PE71S6207	$1,960.27				2
10 GHz	SPDT	TNC Female	F/I, TTL, D, Non-T	60	0.6	12	50	PE71S6200	$1,176.16				3
						28		PE71S6201	$1,193.77				4
			F/Non-T					PE71S6199	$1,486.77				5
	SP4T	N Female	NO/I, TTL, D, Non-T			12		PE71S6184	$1,866.18				6
						28		PE71S6185	$1,866.18				7
						12	160	PE71S6192	$2,146.22				8
			NO/Non-T			28	50	PE71S6183	$1,437.16				9
							160	PE71S6191	$1,869.95				10
	SP6T		NO/I, TTL, D, Non-T				50	PE71S6189	$2,053.24				11
						12	160	PE71S6196	$2,520.34				12
						28		PE71S6197	$2,657.85				13
			NO/Non-T			12	50	PE71S6186	$1,723.58				14
						28		PE71S6187	$1,698.16				15
						12	160	PE71S6194	$2,016.27				16
12.4 GHz	SPDT	N Female	F/I, TTL, D, Non-T	60	0.6	12	160	PE71S6160	$1,397.44				17
						28		PE71S6161	$1,397.44				18
			F/Non-T		0.5		200	PE71S6058	$904.23				19
						12		PE71S6059	$674.65				20
					0.6		50	PE71S6150	$767.82				21
							160	PE71S6158	$1,063.14				22

Switches

1M Life Cycles

Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: Non-Terminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
12.4 GHz	SPDT	N Female	F/Non-T	60	0.6	28	160	PE71S6159	$1,063.14	See Web for Volume Pricing	23
			L/I, TTL, D, S, Non-T		0.5	12	50	PE71S6156	$1,476.58		24
					0.6	28		PE71S6157	$1,400.19		25
			L/S, D, Non-T			12	160	PE71S6164	$1,653.76		26
						28	50	PE71S6155	$1,213.13		27
						12	160	PE71S6162	$1,466.43		28
						28		PE71S6163	$1,411.39		29
	Transfer		F/I, TTL, D, Non-T		0.4	12	50	PE71S6168	$1,697.03		30
						28		PE71S6169	$1,791.99		31
							160	PE71S6177	$1,904.26		32
		TNC Female			0.6	12	50	PE71S6204	$1,643.27		33
						28		PE71S6205	$1,822.58		34
		N Female	F/Non-T		0.4	12		PE71S6166	$1,372.19		35
						28		PE71S6167	$1,448.23		36
							160	PE71S6175	$1,628.08		37
		TNC Female			0.6	12	50	PE71S6202	$1,456.20		38
						28		PE71S6203	$1,535.64		39
		N Female	L/I, TTL, S, D, Non-T		0.4	12		PE71S6172	$2,144.00		40
							160	PE71S6180	$2,392.86		41
						28		PE71S6181	$2,303.04		42
			L/S, D, Non-T			12	50	PE71S6170	$1,779.93		43
						28		PE71S6171	$1,877.03		44
						12	160	PE71S6178	$2,033.08		45
						28		PE71S6179	$2,113.54		46
18 GHz	SPDT	SMA Female	F/Non-T	70	0.4	12	20	PE71S6326	$352.09		47
22 GHz	SPDT	SMA Female	F/T	60	0.6	12	20	PE71S6293	$1,329.93		48
			L/S, D, TTL, I, T			28		PE71S6300	$1,586.88		49
			L/S, D, TTL, T					PE71S6298	$1,493.53		50
	SP4T		L/S, D, T					PE71S6306	$2,475.54		51
			NO/I, T					PE71S6302	$2,102.65		52
			NO/I, TTL, D, T					PE71S6304	$2,649.03		53
			NO/T			12		PE71S6301	$2,102.65		54
	SP6T		L/I, TTL, S, D, T					PE71S6315	$3,277.82		55
						28		PE71S6316	$3,277.82		56
			L/S, D, T			12		PE71S6313	$2,968.40		57
						28		PE71S6314	$2,968.40		58
			NO/Non-T			12		PE71S6130	$1,685.30		59
						28		PE71S6131	$1,575.03		60
			NO/T			12		PE71S6309	$2,475.49		61
						28		PE71S6310	$2,418.24		62
26.5 GHz	SPDT	SMA Female	L/S, D, Non-T	50	0.5	12	20	PE71S6098	$612.21		63
	Transfer		F/Non-T	60				PE71S6110	$1,017.36		64
40 GHz	SPDT	2.92mm Female	F/Non-T	50	0.8	28	10	PE71S6103	$2,280.34		65
			L/I, TTL, S, D, Non-T	55				PE71S6109	$4,280.46		66
			L/S, D, Non-T	50	0.9	12	5	PE71S6106	$3,367.71		67
	SP4T		L/I, TTL, S, D, Non-T		1			PE71S6140	$7,546.95		68
			L/I, TTL, S, D, T				3	PE71S6319	$8,557.95		69
						28		PE71S6320	$8,557.95		70
			L/S, D, RS, T					PE71S6318	$7,766.37		71

See Our Website For Current Pricing & Real-Time Stock Availability!

Switches

1M Life Cycles

Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: Non-Terminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1	2-4	5-9	10+	ROW
40 GHz	SP4T	2.92mm Female	L/S, D, T	50	1	12	3	PE71S6317	$7,766.37	$7,455.72	$7,145.06	$6,834.41	72
			NO/I, TTL, D, Non-T		0.9	28		PE71S6137	$4,663.95	$4,477.39	$4,290.83	$4,104.28	73
	SP6T		L/S, I, RS, T	60	1	12		PE71S6321	$8,613.96	$8,269.40	$7,924.84	$7,580.28	74
						28		PE71S6322	$8,613.96	$8,269.40	$7,924.84	$7,580.28	75
			L/S, TTL, I, RS, T			12		PE71S6323	$9,427.95	$9,050.83	$8,673.71	$8,296.60	76
						28		PE71S6324	$6,593.97	$6,363.18	$6,132.39	$5,934.57	77
			NO/Non-T	50				PE71S6143	$3,819.43	$3,666.65	$3,513.88	$3,361.10	78
	Transfer		L/S, D, Non-T		0.9	12	5	PE71S6122	$3,538.70	$3,397.15	$3,255.60	$3,114.06	79
						28		PE71S6123	$3,405.87	$3,269.64	$3,133.40	$2,997.17	80

2M Life Cycles

Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: Non-Terminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
3 GHz	SPDT	SMA Female	L/Non-T	30		12		PE71S8001	$507.85	See Web for Volume Pricing	81
	SP4T							PE71S8002	$640.47		82
10 GHz	SPDT	N Female	F	70	0.5	12	600	PE71S6426	$777.38		83
12 GHz	SPDT	N Female	F	70	0.5	12	600	PE71S6435	$984.35		84
						28		PE71S6438	$777.38		85
			F/I, TTL, Non-T			12	1000	PE71S6460	$1,335.69		86
			F/Non-T				200	PE71S6348	$749.02		87
						28		PE71S6397	$458.37		88
						12		PE71S6398	$458.37		89
	DPDT		F/I, TTL, Non-T	60	0.7		1000	PE71S6463	$2,049.68		90
			F/Non-T					PE71S6462	$1,763.00		91
	SP4T		NO	70	0.5		600	PE71S6434	$2,249.79		92
			NO/I, Solder Pins, TTL, Non-T	60		28	1000	PE71S6466	$3,225.00		93
			NO/Solder Pins, Non-T			12		PE71S6464	$2,773.50		94
	SP6T		NO/I, Solder Pins, TTL, Non-T					PE71S6465	$3,411.33		95
	Transfer		F/Non-T		0.7	28	200	PE71S6385	$1,122.07		96
								PE71S6403	$821.38		97
			F/TTL, Non-T					PE71S6386	$1,242.55		98
12.4 GHz	SP6T	N Female	L/I, RS, Non-T	60	0.5	12	200	PE71S6072	$3,839.68		99
						28		PE71S6073	$3,524.92		1
	SP12T	SMA Female	L/S, AR, I, D, T		0.6		120	PE71S6082	$8,994.73		2
18 GHz	SPDT	SMA Female	F	65	0.6	28	90	PE71S6429	$368.73		3
					0.35			PE71S6436	$272.07		4
			F/I, Non-T			12	60	PE71S6351	$367.50		5
			F/Non-T					PE71S6347	$291.22		6
						28		PE71S6391	$291.66		7
						12		PE71S6392	$293.10		8
			F/T	60	0.5	28	100	PE71S6060	$1,228.16		9
				65	0.35	12	60	PE71S6354	$1,226.35		10
						28		PE71S6355	$1,293.26		11

2M Life Cycles

Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: Non-Terminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
18 GHz	SPDT	SMA Female	F/T	65	0.35	28	60	PE71S6404	$1,168.18	See Web for Volume Pricing	12
			F/TTL, Non-T			12		PE71S6350	$445.83		13
			L/TTL, T	60	0.5	28	100	PE71S6063	$1,536.57		14
	SP4T		NO/Non-T	80	0.4	12	60	PE71S6363	$1,230.00		15
						28		PE71S6408	$879.11		16
			NO/T			12		PE71S6368	$2,560.92		17
						28		PE71S6369	$2,660.80		18
	SP6T		NO/Non-T			12		PE71S6373	$1,366.22		19
						28		PE71S6409	$1,118.08		20
			NO/T			12		PE71S6380	$3,069.67		21
						28		PE71S6381	$3,069.67		22
			NO/TTL, Non-T			12		PE71S6374	$1,505.46		23
						24		PE71S6375	$1,505.46		24
	SP8T		L/I, RS, T	60	0.6	28	100	PE71S6080	$8,051.13		25
			NO/Non-T	75	0.5	12	60	PE71S6384	$2,436.56		26
	SP10T			55	0.7	28	100	PE71S6076	$4,403.10		27
	SP12T		L/I, RS, T	50	0.8			PE71S6083	$8,921.82		28
	Transfer		F	60	0.5		90	PE71S6433	$672.89		29
			F/Non-T			12	60	PE71S6388	$858.30		30
						24		PE71S6389	$823.93		31
						28	90	PE71S6400	$721.37		32
20 GHz	SP10T	SMA Female	NO/Non-T	70	0.7	28	60	PE71S6410	$3,219.77		33
26.5 GHz	SPDT	SMA Female	F	50	0.6	28	90	PE71S6419	$529.84		34
						12		PE71S6420	$454.40		35
						28		PE71S6421	$452.55		36
						24		PE71S6430	$452.55		37
			F/I, TTL, T			12		PE71S6468	$1,467.38		38
						28		PE71S6469	$1,327.63		39
			F/T			12	50	PE71S6356	$1,329.76		40
						28		PE71S6357	$1,310.14		41
								PE71S6467	$1,164.23		42
			F/TTL,				90	PE71S6422	$609.37		43
						12		PE71S6437	$558.30		44
	DPDT		F/I, TTL, Non-T	60	0.8			PE71S6446	$1,091.13		45
						28		PE71S6447	$1,091.13		46
	SP4T		NO/I, TTL, Solder Pins, T	70	0.7	12		PE71S6472	$3,250.80		47
			NO/Solder Pins, Non-T					PE71S6452	$1,505.00		48
						28		PE71S6453	$1,580.25		49
			NO/T			12	50	PE71S6370	$3,003.87		50
						28		PE71S6371	$2,891.11		51
			NO/TTL,			12	90	PE71S6423	$1,679.88		52
						28		PE71S6424	$1,569.96		53
	SP6T		F/TTL,	50	0.6	12		PE71S6427	$2,691.48		54
				70				PE71S6428	$1,870.52		55
			L/S, RS, D, T	50	0.7	28	40	PE71S6079	$4,796.40		56
			NO/I, Solder Pins, TTL, Non-T	70		12		PE71S6454	$2,342.89		57
						28		PE71S6455	$2,342.18		58
26.5 GHz			NO/T			12	50	PE71S6382	$3,209.95		59
						28		PE71S6383	$3,209.95		60
40 GHz	SPDT	2.92mm Female	F/I, TTL, Non-T	60	0.7	12		PE71S6444	$1,379.58		61

See Our Website For Current Pricing & Real-Time Stock Availability!

Switches

2M Life Cycles

Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: Non-Terminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
40 GHz	SPDT	2.92mm Female	F/Non-T	60	0.7	12		PE71S6443	$1,222.82	See Web for Volume Pricing	62
			L/I, TTL, S, T	50	0.8	28	10	PE71S6064	$3,259.23		63
	DPDT		F/I, TTL, Non-T		1	12		PE71S6451	$3,655.00		64
			F/Non-T			28		PE71S6450	$3,296.68		65
						12		PE71S6476	$2,688.93		66
	SP4T		NO		0.6	28	90	PE71S6431	$3,380.00		67
			NO/I, TTL, + COM, Non-T	60	1.1			PE71S6457	$5,210.16		68
			NO/I, TTL, Non-T	50	1.3	12		PE71S6456	$4,429.00		69
	SP6T		L/I, RS, T		1.1	28	5	PE71S6084	$5,342.71		70
			L/S, RS, D, Non-T					PE71S6078	$3,248.60		71
			NO/+ COM, Non-T	60				PE71S6459	$6,443.31		72
			NO/I, TTL, Non-T	50	1.3	12		PE71S6458	$4,740.75		73
	Transfer		F		0.6		90	PE71S6432	$2,629.30		74
50 GHz	SPDT	2.4mm Female	F/Non-T	60	0.3	28	80	PE71S6329	$1,973.09		75
			L/Non-T		1.1			PE71S6330	$1,576.98		76

2.5M Life Cycles

Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: Non-Terminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
12.4 GHz	Transfer	N Female	F/I, Non-T	60	0.5	28	200	PE71S6070	$1,086.30	See Web for Volume Pricing	77
18 GHz	Transfer	SMA Female	F/Non-T	60	0.5	28	100	PE71S6065	$958.75		78
						12		PE71S6066	$1,039.88		79
			L/I, Non-T			28		PE71S6069	$1,466.36		80
			L/I, S, Non-T					PE71S6067	$1,184.55		81
			L/I, TTL, S, Non-T					PE71S6068	$1,356.89		82
40 GHz	Transfer	2.92mm Female	L/I, S, Non-T	50	0.8	28	10	PE71S6071	$2,002.01		83

5M Life Cycles

Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: Non-Terminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
12 GHz	SPDT	N Female	L/I, Non-T	70	0.5	28	200	PE71S6399	$907.85	See Web for Volume Pricing	84
			L/Non-T			12		PE71S6349	$823.35		85
			L/TTL,			28	600	PE71S6425	$1,210.12		86
	DPDT		L/I, S, TTL, Non-T	60	0.7		1000	PE71S6461	$1,990.77		87
	Transfer		L/Non-T			12	200	PE71S6387	$1,106.87		88
		SMA Female			0.3		75	PE71S6390	$858.83		89
		N Female	L/TTL,		0.7	28	600	PE71S6439	$1,362.66		90
18 GHz	SPDT	SMA Female	L/I, Non-T	65	0.35	12	60	PE71S6353	$358.17		91
						28		PE71S6395	$478.19		92
						12		PE71S6396	$546.42		93

5M Life Cycles

Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: Non-Terminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
18 GHz	SPDT	SMA Female	L/I, T	65	0.35	24	60	PE71S6406	$1,151.64	See Web for Volume Pricing			94
			L/I, TTL, T			28		PE71S6407	$1,334.69				95
			L/Non-T			12		PE71S6352	$328.77				96
			L/S, I, Non-T			28		PE71S6393	$625.11				97
			L/T			12		PE71S6394	$458.42				98
								PE71S6358	$1,320.20				99
						28		PE71S6359	$1,251.90				1
	SP3T		L/Non-T	80	0.4			PE71S6362	$2,026.01				2
	DP3T		L/I, Non-T	65	0.35			PE71S6405	$1,528.10				3
	SP4T		L/T	80	0.4	12		PE71S6364	$2,345.52				4
						28		PE71S6365	$2,345.52				5
	SP6T		NO/Non-T	60	0.5		100	PE71S6074	$1,981.13				6
			L/I, S, AR, D, Non-T					PE71S6077	$3,125.71				7
			L/Non-T	80	0.4		60	PE71S6372	$2,610.59				8
			L/T			12		PE71S6376	$3,237.13				9
						28		PE71S6377	$3,069.67				10
			NO/Non-T	60	0.5		100	PE71S6075	$2,193.30				11
	Transfer		L/I, Non-T				60	PE71S6402	$779.15				12
			L/S, I, Non-T					PE71S6401	$964.84				13
26.5 GHz	SPDT	SMA Female	L/S, D, Non-T	50	0.6	28		PE71S6440	$658.44				14
			L/S, I, TTL, Non-T			12		PE71S6441	$815.21				15
						28		PE71S6442	$856.00				16
			L/S, I, TTL, T	40	0.5	12		PE71S6471	$1,845.43				17
			L/S, TTL, T					PE71S6470	$1,834.25				18
			L/T	50	0.6		50	PE71S6360	$1,337.43				19
						28		PE71S6361	$1,337.43				20
	DPDT		L/S, D, Non-T	60	0.8	12		PE71S6448	$1,316.88				21
			L/S, I, TTL, Non-T			28		PE71S6449	$1,514.43				22
	SP4T		L/S, I, TTL, Solder Pins, T	70	0.7	12		PE71S6473	$3,896.16				23
						28		PE71S6474	$3,896.27				24
			L/T			12	50	PE71S6366	$2,791.49				25
						28		PE71S6367	$3,003.87				26
	SP6T		L/I, TTL, Solder Pins, T					PE71S6475	$3,559.33				27
			L/T			12	50	PE71S6378	$3,209.95				28
						28		PE71S6379	$3,209.95				29
40 GHz	SPDT	2.92mm Female	L/S, I, TTL, Non-T	60	0.7	12		PE71S6445	$1,552.06				30
	SP4T		L/I, S, RS, T 0.05	80	0.5	24	5	PE71S6334	$7,331.31				31
			L/I, S, TTL, RS, T 0.05					PE71S6342	$7,771.24				32
	SP6T		L/I, S, RS, T 0.05		0.9			PE71S6332	$7,820.08				33
			L/I, S, TTL, RS, T 0.05					PE71S6340	$8,195.19				34

10M Life Cycles

Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: Non-Terminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isolation (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1	2-4	5-9	10+	ROW
6 GHz	SP6T	SMA Female	NO/Non-T	70	0.3	28	70	PE71S6085	$1,854.08	$1,779.92	$1,705.75	$1,631.59	35

10M Life Cycles

Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: Non-Terminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isola-tion (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
18 GHz	SPDT	SMA Female	F/Non-T	60	0.35	28	100	PE71S6052	$369.29	See Web for Volume Pricing			36
					0.5	12		PE71S6053	$366.74				37
			L/I, S, Non-T			28		PE71S6054	$562.85				38
						12		PE71S6055	$503.81				39
20 GHz	SPDT	SMA Female	L/I, S, Non-T 0.03	65	0.5	24	1	PE71S6335	$1,561.01				40
			L/I, S, T 0.03					PE71S6337	$2,263.86				41
			L/I, S, TTL, Non-T 0.03					PE71S6336	$1,931.33				42
			L/I, S, TTL, T 0.03					PE71S6338	$2,516.05				43
	SP4T		L/I, S, RS, T 0.03	80	0.6		70	PE71S6333	$5,223.57				44
			L/I, S, TTL, RS, T 0.03					PE71S6341	$5,536.99				45
	SP6T		L/I, S, RS, T 0.03					PE71S6331	$5,803.95				46
			L/I, S, TTL, RS, T 0.03					PE71S6339	$6,152.18				47
26.5 GHz	SP6T	SMA Female	L/GR, Non-T	55	0.6	28	40	PE71S6087	$2,530.74				48
			NO/TTL, Non-T					PE71S6088	$2,624.22				49
40 GHz	SPDT	2.92mm Female	F/I, Non-T	50	0.8	28	10	PE71S6056	$1,343.77				50
			L/I, S, Non-T					PE71S6057	$995.66				51

Special Applications

Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: Non-Terminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isola-tion (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
1 GHz	A/B Coaxial	BNC Female		50	0.7	12	5	PE7100	$621.38	See Web for Volume Pricing			52
		N Female						PE7102	$476.47				53
	A/B Coaxial 75 Ohm							PE7103	$424.67				54
		BNC Female					10	PE7176	$824.33				55

SMT Packaged Electromechanical Switches

Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
NO: Normally Open
NT: Non-Terminated
P: Pulse
Latching
R: Reflective
RS: Reset
S: Self Cut Off
T: Terminated
TTL: TTL Logic

Max Frequency (GHz)	Switch Type	Connector Type	Features	Min Isola-tion (dB)	Max IL (dB)	Voltage (V)	RF Power (W CW)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
8 GHz	SPDT	SMT	F/H, Non-T	30	0.8	24	35	PE71S6092	$318.01	See Web for Volume Pricing			56
			L/H, Non-T	40	0.5	12	5	PE71S6413	$326.22				57
						24		PE71S6414	$326.22				58
18 GHz					1	12	3	PE71S6415	$429.78				59
						24		PE71S6416	$429.78				60
26.5 GHz					1.6		1	PE71S6418	$542.88				61
						12		PE71S6417	$542.88				62

*Available SMA Connectorized Application PWB Option. Model PE71S8001 PWB supports connectorized SPDT. Model PE71S8002 PWB supports Connectorized SP4T.

Waveguide Electromechanical Relay Switches, See Page 377

MANUAL SWITCHES

Manual Switches

Impedance	Connector	Gender	Number of Output Ports	Frequency Range (MHz.)	Maximum Power	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
50 Ohm	N	Female to		DC - 1,300	500 Watt	PE7139	$261.10		See Web for Volume Pricing		63
						PE7140	$415.15				64
	SMA			DC - 22,000	50 Watt	PE7SM1000A	$897.36				65

PIN Diode Switches

SPST

Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	10 MHz - 1	80	1.3	200	0.1	Solder Pin	SMA Female	PE71S6230	$1,830.96	$1,757.72	$1,684.48	$1,611.24	66
	50 MHz - 26.5	30	5	150	0.5			PE71S2008	$5,973.77	$5,734.82	$5,495.87	$5,256.92	67
	50 MHz - 40	25	7.5		1		2.92mm Female	PE71S2012	$6,347.90	$6,093.98	$5,840.07	$5,586.15	68
	50 MHz - 67		9.5		0.5		1.85mm Female	PE71S2024	$8,028.13	$7,707.00	$7,385.88	$7,064.75	69
	500 MHz - 18	55	3.5	100	0.1		SMA Female	PE71S6209	$2,996.48	$2,876.62	$2,756.76	$2,636.90	70
	500 MHz - 40		5.5				2.92mm Female	PE71S6214	$4,343.49	$4,169.75	$3,996.01	$3,822.27	71
	1 - 2	80	0.9	50			SMA Female	PE71S6231	$2,752.66	$2,642.55	$2,532.45	$2,422.34	72
	1 - 18	65	3					PE71S6236	$4,511.17	$4,330.72	$4,150.28	$3,969.83	73
	2 - 4	75	1.1					PE71S6232	$2,109.62	$2,025.24	$1,940.85	$1,856.47	74
	2 - 26.5	25	4.5	150	1			PE71S2016	$5,808.26	$5,575.93	$5,343.60	$5,111.27	75
	2 - 40	30	5				2.92mm Female	PE71S2020	$5,874.47	$5,639.49	$5,404.51	$5,169.53	76
	4 - 8	75	1.8	50	0.1		SMA Female	PE71S6233	$2,801.33	$2,689.28	$2,577.22	$2,465.17	77
	8 - 12	70						PE71S6234	$2,539.71	$2,438.12	$2,336.53	$2,234.94	78
	12 - 18	65	2.8					PE71S6235	$2,618.48	$2,513.74	$2,409.00	$2,304.26	79
Reflective	10 MHz - 1	80	1	200	0.1	Solder Pin	SMA Female	PE71S6258	$1,752.20	$1,682.11	$1,612.02	$1,541.94	80
	50 MHz - 26.5	20	5	150	1			PE71S2007	$5,152.69	$4,946.58	$4,740.47	$4,534.37	81
	50 MHz - 40	25	6.5				2.92mm Female	PE71S2011	$5,525.71	$5,304.68	$5,083.65	$4,862.62	82
	50 MHz - 67	20	8.5		0.5		1.85mm Female	PE71S2023	$6,815.00	$6,542.40	$6,269.80	$5,997.20	83
	500 MHz - 18	55	3	100	0.1		SMA Female	PE71S6220	$2,766.78	$2,656.11	$2,545.44	$2,434.77	84
	500 MHz - 40		5				2.92mm Female	PE71S6225	$3,229.77	$3,100.58	$2,971.39	$2,842.20	85
	1 - 2	80	0.75	50			SMA Female	PE71S6259	$1,870.66	$1,795.83	$1,721.01	$1,646.18	86
	1 - 18	65	2.5					PE71S6264	$2,760.23	$2,649.82	$2,539.41	$2,429.00	87
	2 - 4	75	0.85					PE71S6260	$2,034.96	$1,953.56	$1,872.16	$1,790.76	88
	2 - 26.5	20	4.5	150	1			PE71S2015	$4,849.72	$4,655.73	$4,461.74	$4,267.75	89
	2 - 40		4				2.92mm Female	PE71S2019	$5,040.68	$4,839.05	$4,637.43	$4,435.80	90
	4 - 8	75	1.5	50	0.1		SMA Female	PE71S6261	$2,277.63	$2,186.52	$2,095.42	$2,004.31	91
	8 - 12	70	1.8					PE71S6262	$2,333.65	$2,240.30	$2,146.96	$2,053.61	92
	12 - 18	65	2.5					PE71S6263	$2,408.33	$2,312.00	$2,215.66	$2,119.33	93

SPDT



Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	5 MHz - 2.15	70	2.5	100,000	0.1	D-Sub	F Female	PE71S2043	$1,432.15	$1,374.86	$1,317.58	$1,260.29	94
	5 MHz - 3	80	3.5	10,000	1		SMA Female	PE71S2036	$1,222.80	$1,173.89	$1,124.98	$1,076.06	95
	10 MHz - 1		1.3	200	0.1	Solder Pin		PE71S6237	$2,130.20	$2,044.99	$1,959.78	$1,874.58	96
	20 MHz - 4.3		3	10,000	1	D-Sub		PE71S2035	$1,222.80	$1,173.89	$1,124.98	$1,076.06	97
	70 MHz - 26.5	55	5	100	0.5	SMA Female		PE71S2010	$9,473.95	$9,094.99	$8,716.03	$8,337.08	98
	70 MHz - 40		7			2.92mm Female	2.92mm Female	PE71S2014	$9,758.18	$9,367.85	$8,977.53	$8,587.20	99
	100 MHz - 67	40	10.5			SMA Female	1.85mm Female	PE71S2050	$8,233.11	$7,739.12	$7,327.47	$6,998.14	1
	500 MHz - 18	55	3.75		0.1	Solder Pin	SMA Female	PE71S6210	$3,405.96	$3,269.72	$3,133.48	$2,997.24	2
	500 MHz - 40	60	6	50			2.92mm Female	PE71S6215	$5,897.28	$5,661.39	$5,425.50	$5,189.61	3
	800 MHz - 2.7	75	0.8	10,000	100		SMA Female	PE71S2041	$3,837.67	$3,684.16	$3,530.66	$3,377.15	4
	1 - 18	65	3.5	100	0.1			PE71S6241	$3,130.34	$3,005.13	$2,879.91	$2,754.70	5
	2 - 4	75	1.2		0.5	Pin		PE71S6208	$2,441.30	$2,343.65	$2,246.00	$2,148.34	6
	2 - 26.5	60	4			SMA Female		PE71S2018	$8,599.40	$8,255.42	$7,911.45	$7,567.47	7
	2 - 40	55	5.5			2.92mm Female	2.92mm Female	PE71S2022	$8,961.20	$8,602.75	$8,244.30	$7,885.86	8
	4 - 8	70	1.9		0.1	Solder Pin	SMA Female	PE71S6238	$2,910.54	$2,794.12	$2,677.70	$2,561.28	9
	8 - 12		2.2					PE71S6239	$4,557.14	$4,374.85	$4,192.57	$4,010.28	10
	12 - 18		3.5					PE71S6240	$2,917.72	$2,801.01	$2,684.30	$2,567.59	11
Reflective	DC - 6	25	1.3	100	40		SMA Female	PE71S1100	$3,027.93	$2,906.81	$2,785.70	$2,664.58	12
								PE71S1105	$3,190.80	$3,063.17	$2,935.54	$2,807.90	13
	DC - 12		2	150	25			PE71S1101	$2,912.28	$2,795.79	$2,679.30	$2,562.81	14
								PE71S1106	$3,075.16	$2,952.15	$2,829.15	$2,706.14	15
	DC - 18	23	2.3	100	10			PE71S1102	$3,080.04	$2,956.84	$2,833.64	$2,710.44	16
								PE71S1107	$3,242.93	$3,113.21	$2,983.50	$2,853.78	17
	10 MHz - 1	80	1.1	200	0.1	Solder Pin		PE71S6265	$1,945.35	$1,867.54	$1,789.72	$1,711.91	18
	20 MHz - 500 MHz	50	0.5	40,000	150			PE71S2039	$3,465.74	$3,327.11	$3,188.48	$3,049.85	19
	20 MHz - 1	40	0.75					PE71S2040	$3,465.74	$3,327.11	$3,188.48	$3,049.85	20
	20 MHz - 2.5	50	1	10,000	25			PE71S2042	$3,113.43	$2,988.89	$2,864.36	$2,739.82	21
	30 MHz - 530 MHz	60		200	5			PE71S2047	$791.20	Call	Call	Call	22
	50 MHz - 1.5				4			PE71S2048	$776.25	Call	Call	Call	23
	70 MHz - 26.5	30	3.5	100	0.5	SMA Female		PE71S2009	$7,280.98	$6,989.74	$6,698.50	$6,407.26	24
	70 MHz - 40		5.5			2.92mm Female	2.92mm Female	PE71S2013	$7,653.99	$7,347.83	$7,041.67	$6,735.51	25
	100 MHz - 500 MHz	55	0.5	40,000	250	Solder Pin	SMA Female	PE71S2038	$3,286.45	$3,154.99	$3,023.53	$2,892.08	26
	500 MHz - 6	35	1.5	250	100		N Female	PE71S1103	$3,583.33	$3,440.00	$3,296.66	$3,153.33	27
								PE71S1108	$3,746.22	$3,596.37	$3,446.52	$3,296.67	28
	500 MHz - 18	55	3.2	100	0.1	Solder Pin	SMA Female	PE71S6221	$3,155.11	$3,028.91	$2,902.70	$2,776.50	29
	500 MHz - 40		5.5	50			2.92mm Female	PE71S6226	$3,543.42	$3,419.40	$3,295.38	$3,189.08	30
	1 - 18	65	2.5	100			SMA Female	PE71S6269	$3,006.58	$2,886.32	$2,766.05	$2,645.79	31
	2 - 4	75	0.9		1			PE71S6219	$2,240.30	$2,150.69	$2,061.08	$1,971.46	32
	2 - 26.5	30	3			SMA Female		PE71S2017	$8,162.23	$7,835.74	$7,509.25	$7,182.76	33
	2 - 40		4		0.5	2.92mm Female	2.92mm Female	PE71S2021	$8,409.19	$8,072.82	$7,736.45	$7,400.09	34
	4 - 8	70	1.6		0.1	Solder Pin	SMA Female	PE71S6266	$2,520.34	$2,419.53	$2,318.71	$2,217.90	35
	8 - 12		1.9					PE71S6267	$2,719.52	$2,610.74	$2,501.96	$2,393.18	36
	12 - 18		2.5					PE71S6268	$2,692.10	$2,584.42	$2,476.73	$2,369.05	37

SP3T

Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	10 MHz - 1	60	1.4	200	0.1	Solder Pin	SMA Female	PE71S6242	$2,296.31	$2,204.46	$2,112.61	$2,020.75	38
	500 MHz - 18	55	3.8	100				PE71S6211	$4,210.43	$4,042.01	$3,873.60	$3,705.18	39
	500 MHz - 40	60	6	50			2.92mm Female	PE71S6216	$6,031.13	$5,789.88	$5,548.64	$5,307.39	40
	1 - 2		1.25	100			SMA Female	PE71S6243	$2,505.42	$2,405.20	$2,304.99	$2,204.77	41
	1 - 18	65	3.75					PE71S6248	$3,278.12	$3,147.00	$3,015.87	$2,884.75	42
	2 - 4	75	1.5					PE71S6244	$2,669.69	$2,562.90	$2,456.11	$2,349.33	43
	4 - 8		2.5					PE71S6245	$3,035.84	$2,914.41	$2,792.97	$2,671.54	44
	8 - 12	70	2.8					PE71S6246	$3,619.53	$3,474.75	$3,329.97	$3,185.19	45
	12 - 18		3.75					PE71S6247	$3,088.65	$2,965.10	$2,841.56	$2,718.01	46
Reflective	10 MHz - 1	60	1	200	0.1	Solder Pin	SMA Female	PE71S6270	$2,342.84	$2,249.13	$2,155.41	$2,061.70	47
	500 MHz - 18	55	3.2	100				PE71S6222	$3,528.48	$3,387.34	$3,246.20	$3,105.06	48
	500 MHz - 40		5.5	50			2.92mm Female	PE71S6227	$5,610.98	$5,386.54	$5,162.10	$4,937.66	49
	1 - 2	60	1	100			SMA Female	PE71S6271	$2,430.73	$2,333.50	$2,236.27	$2,139.04	50
	1 - 18	65	2.75					PE71S6276	$3,155.47	$3,029.25	$2,903.03	$2,776.81	51
	2 - 4	75	1.2					PE71S6272	$2,595.03	$2,491.23	$2,387.43	$2,283.63	52
	4 - 8		2					PE71S6273	$2,804.11	$2,691.95	$2,579.78	$2,467.62	53
	8 - 12	70	2.4					PE71S6274	$3,830.08	$3,676.88	$3,523.67	$3,370.47	54
	12 - 18		2.75					PE71S6275	$2,968.40	$2,849.66	$2,730.93	$2,612.19	55

SP4T

Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	5 MHz - 2.15	70	2.5	100,000	0.1	D-Sub	F Female	PE71S2044	$1,959.79	$1,881.40	$1,803.01	$1,724.62	56
	5 MHz - 3		3.5	10,000	1		SMA Female	PE71S2037	$1,702.13	$1,634.04	$1,565.96	$1,497.87	57
	10 MHz - 1	60	1.5	200	0.1	Solder Pin		PE71S6249	$2,580.08	$2,476.88	$2,373.67	$2,270.47	58
	500 MHz - 18	55	3.8	100				PE71S6212	$5,453.13	$5,235.00	$5,016.88	$4,798.75	59
	500 MHz - 40	60	8	50			2.92mm Female	PE71S6217	$8,940.43	$8,582.81	$8,225.20	$7,867.58	60
	1 - 2		1.2	100			SMA Female	PE71S6250	$2,823.35	$2,710.42	$2,597.48	$2,484.55	61
	1 - 18	70	3.75					PE71S6255	$3,566.16	$3,423.51	$3,280.87	$3,138.22	62
	2 - 4	75	1.5					PE71S6251	$2,953.48	$2,835.34	$2,717.20	$2,599.06	63
	4 - 8	70	2.2					PE71S6252	$3,155.11	$3,028.91	$2,902.70	$2,776.50	64
	8 - 12		2.6					PE71S6253	$3,929.08	$3,771.92	$3,614.75	$3,457.59	65
	12 - 18		3.75					PE71S6254	$3,326.85	$3,193.78	$3,060.70	$2,927.63	66
Reflective	DC - 6	25	2	100	40		SMA Female	PE71S1104	$4,844.02	$4,650.26	$4,456.50	$4,262.74	67
								PE71S1109	$5,006.90	$4,806.62	$4,606.35	$4,406.07	68
	10 MHz - 1	60	1.2	200	0.1	Solder Pin		PE71S6277	$2,505.79	$2,405.56	$2,305.33	$2,205.10	69
	500 MHz - 18	55	3.2	100				PE71S6223	$4,947.35	$4,749.46	$4,551.56	$4,353.67	70
	500 MHz - 40		7.5	50			2.92mm Female	PE71S6228	$7,379.92	$7,084.72	$6,789.53	$6,494.33	71
	1 - 2	60	1	100			SMA Female	PE71S6278	$2,707.41	$2,599.11	$2,490.82	$2,382.52	72
	1 - 18	70	3					PE71S6283	$3,438.87	$3,301.32	$3,163.76	$3,026.21	73
	2 - 4	75	1.1					PE71S6279	$2,878.79	$2,763.64	$2,648.49	$2,533.34	74
	2 - 6	70	2	50				PE71S6284	$2,781.71	$2,670.44	$2,559.17	$2,447.90	75
	4 - 8		1.8	100				PE71S6280	$3,080.42	$2,957.20	$2,833.99	$2,710.77	76
	6 - 12		2.5	50				PE71S6285	$2,856.39	$2,742.13	$2,627.88	$2,513.62	77
	8 - 12		2.2	100				PE71S6281	$3,177.51	$3,050.41	$2,923.31	$2,796.21	78
	12 - 18		3					PE71S6282	$3,252.17	$3,122.08	$2,992.00	$2,861.91	79

SP5T

Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	100 MHz - 20	65	3.9	75	0.5	Solder Pin	SMA Female	PE71S2045	$4,680.34	$4,493.13	$4,305.91	$4,118.70	80

SP6T

Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	100 MHz - 20	65	4.2	75	0.5	Solder Pin	SMA Female	PE71S2046	$5,195.73	$4,987.90	$4,780.07	$4,572.24	81

SP8T

Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	100 MHz - 20	65	6	100	0.5	Solder Pin	SMA Female	PE71S2033	$8,682.25	$8,334.96	$7,987.67	$7,640.38	82
	500 MHz - 18	55	4.5	50	0.1			PE71S6213	$8,669.76	$8,322.97	$7,976.18	$7,629.39	83
	500 MHz - 40	50	10				2.92mm Female	PE71S6218	$10,611.63	$10,187.16	$9,762.70	$9,338.23	84
Reflective	500 MHz - 18	55	4	100	0.1	Solder Pin	SMA Female	PE71S6224	$8,367.25	$8,032.56	$7,697.87	$7,363.18	85
	500 MHz - 40	45	9	50			2.92mm Female	PE71S6229	$10,377.56	$9,962.46	$9,547.36	$9,132.25	86

SP12T

Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	100 MHz - 20	65	6	100	0.5	Solder Pin	SMA Female	PE71S2034	$11,410.95	$10,954.51	$10,498.07	$10,041.64	87

Transfer

Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Absorptive	10 MHz - 1	80	1.3	100	2	Solder Pin	SMA Female	PE71S6286	$3,232.73	$3,103.42	$2,974.11	$2,844.80	88
	1 - 2		1		1			PE71S6287	$3,901.25	$3,745.20	$3,589.15	$3,433.10	89
	1 - 18	65	3.1		0.5			PE71S6292	$5,870.86	$5,636.03	$5,401.19	$5,166.36	90
	2 - 4	75	1.2		1			PE71S6288	$3,626.47	$3,481.41	$3,336.35	$3,191.29	91
	4 - 8		1.9					PE71S6289	$3,603.17	$3,459.04	$3,314.92	$3,170.79	92
	8 - 12	70	2.2		0.5			PE71S6290	$3,812.25	$3,659.76	$3,507.27	$3,354.78	93
	12 - 18	65	3					PE71S6291	$4,349.92	$4,175.92	$4,001.93	$3,827.93	94

High Isolation PIN Diode Switches

Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
SPST	0 - 20	65	6	8.5	Solder Pin	SMA Female	PE71S5001	$6,916.43	$6,639.77	$6,363.12	$6,086.46	95
SPDT	0 - 18		3	12			PE71S5005	$7,188.18	$6,900.65	$6,613.13	$6,325.60	96
	0 - 20	35	4	5			PE71S5000	$4,610.96	$4,426.52	$4,242.08	$4,057.64	97
	1 - 2	90	1	75	Solder Terminals		PE71S5002	$2,032.59	$1,951.29	$1,869.98	$1,788.68	98
SP4T	0 - 20	38	3.8		Solder Pin		PE71S5006	$7,793.23	$7,481.50	$7,169.77	$6,858.04	99
	2 - 6	80	1.8	35	Solder Terminals		PE71S5003	$2,657.85	$2,551.54	$2,445.22	$2,338.91	1
	6 - 12	75	2.5	40			PE71S5004	$2,862.58	$2,748.08	$2,633.57	$2,519.07	2

High Isolation USB PIN Diode Switches

Switch Type	Frequency Band (GHz.)	Insertion Loss (dB)	Isolation (dB)	Switching Speed (µs)	Model No	1	2-4	5-9	10+	ROW
USB	0.5 - 18.0	6	60	6,000	PE71S3900	$3,700.31	$3,552.30	$3,404.29	$3,256.27	3
	0.5 - 40.0				PE71S3901	$5,047.40	$4,845.50	$4,643.61	$4,441.71	4

GaN High Power Switches

Switch Design	Freq. (GHz.)	Typ Iso (dB)	Typ IL (dB)	Switch Time (ns)	Max Input Power (dB)	TTL Control	Conn. Type	Model No	1	2-4	5-9	10+	ROW
Reflective	DC - 6	33	0.9	100	46	Solder Pin	SMA	PE71S1100	$3,027.93	$2,906.81	$2,785.70	$2,664.58	5
								PE71S1105	$3,190.80	$3,063.17	$2,935.54	$2,807.90	6
		36	1.3					PE71S1104	$4,844.02	$4,650.26	$4,456.50	$4,262.74	7
								PE71S1109	$5,006.90	$4,806.62	$4,606.35	$4,406.07	8
	DC - 12	32	1.5		44			PE71S1106	$3,075.16	$2,952.15	$2,829.15	$2,706.14	9
								PE71S1101	$2,912.28	$2,795.79	$2,679.30	$2,562.81	10
	DC - 18	30	1.3	50	40			PE71S1102	$3,080.04	$2,956.84	$2,833.64	$2,710.44	11
								PE71S1107	$3,242.93	$3,113.21	$2,983.50	$2,853.78	12
	0.5 - 6	43	1.2	100	50		N Type	PE71S1103	$3,583.33	$3,440.00	$3,296.66	$3,153.33	13
								PE71S1108	$3,746.22	$3,596.37	$3,446.52	$3,296.67	14

INDEX GUIDE TO
SYNTHESIZERS AND OSCILLATORS

SYNTHESIZERS 336

VOLTAGE CONTROLLED OSCILLATORS 337

0.175" Ultra Small Commercial Surface Mount Packaged VCO 337

0.5" Commercial Surface Mount Packaged VCO 337

0.5" Commercial Surface Mount Packaged VCO w/ Integrated Buffer Amps 338

0.5" Commercial Surface Mount Packaged VCO w/ Low Noise 338

0.5" Commercial Surface Mount Packaged VCO w/ Modulation Input Port 339

0.5" Hermatically Sealed MIL Grade Surface Mount Packaged VCO 339

Connectorized Packaged VCO w/ Field Replaceable Connectors 339

Hi Rel Hermatic Buffer Amp 340

Coaxial Packaged Commercial Standard 339

Phase Locked Orscillators 341

Phase Locked Crystal Oscillators 341

Reference Oscillators 340

TCXO Oscillators 340

SYNTHESIZERS

Type	Freq. Band (MHz.)	Typ Ref. Freq. (MHz.)	Ph. Noise @100kHz Offset (dBc/Hz)	Output Power (dBm)	2nd Harmonic	Output Connector	Model No	1	2-4	5-9	10+	ROW
Serial, TTL	2,000 - 6,000	10	-94	14 to 17	-22	SMA Female	PE11S1002	$10,245.68	$9,835.85	$9,426.03	$9,016.20	1
USB	25 - 6,000	50	-86	-40 to 20	-25		PE11S3901	$6,584.09	$6,320.73	$6,057.36	$5,794.00	2
	35 - 4,400		-103	-20 to 10	-30		PE11S3900	$1,910.11	$1,833.71	$1,757.30	$1,680.90	3
	5,000 - 10,000		-72	-15 to 18	-25		PE11S3902	$7,784.34	$7,472.97	$7,161.59	$6,850.22	4
	10,000 - 20,000		-80	-19 to 18	-15		PE11S3903	$8,284.00	$7,994.06	$7,704.12	$7,455.60	5
	21,000 - 24,000		-88	-17 to 17	-22		PE11S3904	$6,173.89	$5,926.93	$5,679.98	$5,433.02	6
	24,000 - 27,000		-75	14 to 17			PE11S3905	$6,642.30	$6,376.61	$6,110.92	$5,845.22	7

0.175” Ultra Small Commercial Surface Mount Packaged VCO

Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1-24	25-49	50-99	100+	ROW
125 - 250	DC - 18	8	5	-107	-10	0.5	3	PE1V21000	Call	Call	Call	Call	8
								PE2V000	$107.29	$101.93	$96.56	$92.27	9
200 - 400	DC - 5	6	3	-95	-14	4	7	PE1V21001	Call	Call	Call	Call	10
								PE2V001	$111.57	$105.99	$100.41	$95.95	11
250 - 500	DC - 20	8	5	-107	-8	1	3	PE1V21002	Call	Call	Call	Call	12
								PE2V002	$107.29	$101.93	$96.56	$92.27	13
500 - 1,000	DC - 19	6	10	-97	-10	4	10	PE1V21003	Call	Call	Call	Call	14
								PE2V003	$111.57	$105.99	$100.41	$95.95	15
800 - 1,600	DC - 18	11	5	-93	-17	4	20	PE1V21004	Call	Call	Call	Call	16
								PE2V004	$142.83	$135.69	$128.55	$122.83	17
1,000 - 2,000	DC - 20	10	12	-90	-7	2	20	PE1V21005	Call	Call	Call	Call	18
								PE2V005	$107.29	$101.93	$96.56	$92.27	19
2,000 - 2,750	DC - 10	11	11	-86	-17	6	22	PE1V21006	Call	Call	Call	Call	20
								PE2V006	$107.29	$101.93	$96.56	$92.27	21
2,000 - 3,000	DC - 20	9	12	-87	-14	2	24	PE1V21007	Call	Call	Call	Call	22
								PE2V007	$111.57	$105.99	$100.41	$95.95	23
3,120 - 3,920	DC - 11	8	10	-87	-22	10	22	PE1V21008	Call	Call	Call	Call	24
								PE2V008	$107.29	$101.93	$96.56	$92.27	25
3,570 - 4,580	DC - 11.5	8	12	-83	-17	4	15	PE1V21009	Call	Call	Call	Call	26
								PE2V009	$109.92	$104.42	$98.93	$94.53	27
4,400 - 5,000	DC - 4.5	1	5	-85	-17	5	18	PE1V21010	Call	Call	Call	Call	28
								PE2V010	$107.81	$102.42	$97.03	$92.72	29
4,800 - 5,200	DC - 3	1	3.3	-80	-20	4	25	PE1V21011	Call	Call	Call	Call	30
								PE2V011	$107.81	$102.42	$97.03	$92.72	31
4,800 - 5,700	DC - 11	8	12	-84	-20	2	20	PE1V21012	Call	Call	Call	Call	32
								PE2V012	$111.57	$105.99	$100.41	$95.95	33
5,180 - 5,805	DC - 10	6	11	-83	-20	5	25	PE1V21013	Call	Call	Call	Call	34
								PE2V013	$111.57	$105.99	$100.41	$95.95	35
5,400 - 5,900	DC - 10	8.5	11	-84	-25	5	25	PE1V21014	Call	Call	Call	Call	36
								PE2V014	$112.62	$106.99	$101.36	$96.85	37
6,100 - 7,000	DC - 10	5.5	5	-76	-30	5	15	PE1V21015	Call	Call	Call	Call	38
								PE2V015	$109.92	$104.42	$98.93	$94.53	39
7,390 - 8,060	DC - 9	4	5	-75	-22	10	40	PE1V21016	Call	Call	Call	Call	40
								PE2V016	$111.57	$105.99	$100.41	$95.95	41
8,300 - 9,100	DC - 10	1	5	-73	-25	5	20	PE1V21017	Call	Call	Call	Call	42
								PE2V017	$111.57	$105.99	$100.41	$95.95	43
9,000 - 10,000	DC - 11	7	12	-78	-30	15	50	PE1V21018	Call	Call	Call	Call	44
								PE2V018	$111.57	$105.99	$100.41	$95.95	45
10,000 - 11,000	DC - 11	4	12	-72	-40	15	70	PE1V21019	Call	Call	Call	Call	46
								PE2V019	$111.57	$105.99	$100.41	$95.95	47

0.5” Commercial Surface Mount Packaged VCO

Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1-24	25-49	50-99	100+	ROW
10 - 20	DC - 20	10	15	-120	-11	0.02	0.05	PE1V11000	$107.63	$102.25	$96.87	$92.56	48
18 - 30	DC - 12	12	12	-120	-13	0.03	0.07	PE1V11001	$107.63	$102.25	$96.87	$92.56	49
25 - 50	DC - 15	11.5	15	-120	-12	0.05	0.03	PE1V11002	$105.06	$99.81	$94.55	$90.35	50
30 - 60	DC - 15	11	15	-119	-14	0.05	0.05	PE1V11003	$103.09	$97.94	$92.78	$88.66	51
40 - 80	DC - 20	12	15	-117	-14	0.05	0.05	PE1V11004	$107.63	$102.25	$96.87	$92.56	52
40 - 100	DC - 20	11.5	15	-118	-14	0.2	0.1	PE1V11005	$103.09	$97.94	$92.78	$88.66	53
50 - 100	DC - 20	12	15	-115	-12	0.05	0.1	PE1V11006	$105.06	$99.81	$94.55	$90.35	54
60 - 120	DC - 18.5	11	15	-114	-20	0.2	0.1	PE1V11007	$103.09	$97.94	$92.78	$88.66	55

* Phase Noise measured at 10 KHz offset frequency

0.5” Commercial Surface Mount Packaged VCO

Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1-24	25-49	50-99	100+	ROW
75 - 150	DC - 18	11	15	-110	-20	0.2	0.4	PE1V11008	$105.06	$99.81	$94.55	$90.35	56
100 - 200	DC - 18	11	15	-113	-12	0.2	0.1	PE1V11009	$103.09	$97.94	$92.78	$88.66	57
150 - 300	DC - 20	11	15	-108	-14	1	2	PE1V11010	$107.63	$102.25	$96.87	$92.56	58
200 - 400	DC - 20	11	15	-106	-14	0.4	0.2	PE1V11011	$185.76	$176.47	$167.18	$159.75	59
300 - 400	DC - 9	11	15	-102	-18	0.6	0.5	PE1V11012	$107.63	$102.25	$96.87	$92.56	60
400 - 600	DC - 15	11	15	-102	-15	1	1.5	PE1V11013	$103.09	$97.94	$92.78	$88.66	61
400 - 800	DC - 9	8	5	-96	-14	3	1.3	PE1V11014	$103.09	$97.94	$92.78	$88.66	62
500 - 900	DC - 11.5	12	12	-95	-14	1.5	1.5	PE1V11015	$103.09	$97.94	$92.78	$88.66	63
600 - 1,000	DC - 20	12.5	15	-96	-15	0.8	0.7	PE1V11016	$107.11	$101.75	$96.40	$92.11	64
800 - 1,200	DC - 20	11.5	15	-95	-12	0.8	2.5	PE1V11017	$107.63	$102.25	$96.87	$92.56	65
1,200 - 1,800	DC - 20	11	15	-89	-12	0.5	3	PE1V11018	$107.63	$102.25	$96.87	$92.56	66
1,350 - 1,650	DC - 18	10	15		-12	1.5		PE1V11019	$103.09	$97.94	$92.78	$88.66	67
1,500 - 2,100	DC - 18	10	15		-12			PE1V11020	$103.09	$97.94	$92.78	$88.66	68
1,500 - 2,500	DC - 16	10	15		-12			PE1V11021	$107.63	$102.25	$96.87	$92.56	69
2,000 - 2,750	DC - 10	7	11		-12			PE1V11022	$107.63	$102.25	$96.87	$92.56	70
2,570 - 3,300	DC - 10	5	11		-15			PE1V11023	$107.63	$102.25	$96.87	$92.56	71
3,000 - 3,500	DC - 10	10	11	-81	-16	2.5	12	PE1V11024	$103.09	$97.94	$92.78	$88.66	72
3,120 - 3,870	DC - 10	5	11		-15			PE1V11025	$107.63	$102.25	$96.87	$92.56	73
4,000 - 5,000	DC - 15	8	15		-18			PE1V11026	$107.63	$102.25	$96.87	$92.56	74
4,260 - 5,000	DC - 10	7	11		-18			PE1V11027	$105.06	$99.81	$94.55	$90.35	75

0.5” Commercial Surface Mount Packaged VCO w/ Integrated Buffer Amps

Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1-24	25-49	50-99	100+	ROW
510 - 550	DC - 3.5	6.5	5	-106	-22	1.5	0.8	PE1V14000	$103.09	$97.94	$92.78	$88.66	76
950 - 1,100	DC - 4.5	9	5	-104	-18	0.8	0.3	PE1V14001	$103.09	$97.94	$92.78	$88.66	77
1,570 - 1,850	DC - 4.5	5	5	-101	-18	1.8	0.2	PE1V14002	$107.63	$102.25	$96.87	$92.56	78
1,600 - 3,200	DC - 20	6	5	-89	-14	4	10	PE1V14003	$107.11	$101.75	$96.40	$92.11	79
1,700 - 1,850	DC - 4.5	3.5	5	-100	-40	0.8	0.2	PE1V14004	$103.09	$97.94	$92.78	$88.66	80
1,800 - 2,000	DC - 4.5	4.5	5	-100	-20	1.5	0.6	PE1V14005	$103.09	$97.94	$92.78	$88.66	81
1,900 - 2,100	DC - 4.5	4.5	5	-102	-40	3	0.3	PE1V14006	$103.09	$97.94	$92.78	$88.66	82
2,100 - 2,300	DC - 4.5	4.5	5	-101	-35	2.5	0.3	PE1V14007	$107.63	$102.25	$96.87	$92.56	83
2,800 - 3,000	DC - 4.5	-2	5	-93	-25	2	0.8	PE1V14008	$103.09	$97.94	$92.78	$88.66	84
4,130 - 4,350	DC - 8	7.5	8	-98	-30	4	6	PE1V14009	$103.09	$97.94	$92.78	$88.66	85
4,770 - 5,010	DC - 7.5	5	8	-98	-20	4	4	PE1V14010	$103.09	$97.94	$92.78	$88.66	86

0.5” Commercial Surface Mount Packaged VCO w/ Low Noise

Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1-24	25-49	50-99	100+	ROW
305 - 425	DC - 19.5	8	5	-117	-40	1.5	4	PE1V15000	$103.09	$97.94	$92.78	$88.66	87
850 - 900	DC - 4.5	1.5	5	-113	-45	0.3	0.2	PE1V15001	$107.11	$101.75	$96.40	$92.11	88

* Phase Noise measured at 10 KHz offset frequency

0.5” Commercial Surface Mount Packaged VCO w/ Modulation Input Port

Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1-9	10-24	25-49	50+	ROW
130 - 175	DC - 15	6.5	5	-125	-25	0.1	0.2	PE1V12000	$122.00	$115.90	$109.80	$104.92	89
195 - 240	DC - 15	8.5	5	-125	-15	0.2	0.05	PE1V12001	$122.00	$115.90	$109.80	$104.92	90
243 - 270	DC - 9.5	10	8	-120	-38	0.05	0.2	PE1V12002	$126.76	$120.42	$114.08	$109.01	91
260 - 280	DC - 10	8	5	-123	-15	0.1	0.1	PE1V12003	$122.00	$115.90	$109.80	$104.92	92
380 - 400	DC - 10	4.5	5	-124	-20	0.2	0.1	PE1V12004	$122.00	$115.90	$109.80	$104.92	93
400 - 430	DC - 10	3.5	5	-123	-25	0.1	0.05	PE1V12005	$122.00	$115.90	$109.80	$104.92	94
430 - 470	DC - 10	3.5	5	-122	-25	0.2	0.05	PE1V12006	$122.00	$115.90	$109.80	$104.92	95
465 - 525	DC - 15	3.5	5	-122	-18	0.1	0.2	PE1V12007	$126.76	$120.42	$114.08	$109.01	96
650 - 700	DC - 10	7.5	8	-121	-25	0.2	0.1	PE1V12008	$122.00	$115.90	$109.80	$104.92	97

0.5” Hermatically Sealed MIL Grade Surface Mount Packaged VCO

Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1-9	10-24	25-49	50+	ROW
10 - 20	DC - 20	10	15	-120	-11	0.02	0.05	PE1V13000	$454.63	$431.90	$409.17	$390.98	98
18 - 30	DC - 12	12	12	-120	-13	0.03	0.07	PE1V13001	$454.63	$431.90	$409.17	$390.98	99
25 - 50	0.5 - 20	11.5	15	-114	-10	0.1	0.1	PE1V13002	$454.63	$431.90	$409.17	$390.98	1
30 - 60	DC - 15	11	15	-119	-14	0.05	0.05	PE1V13003	$454.63	$431.90	$409.17	$390.98	2
40 - 80	DC - 20	12	15	-117	-14	0.05	0.05	PE1V13004	$454.63	$431.90	$409.17	$390.98	3
40 - 100	DC - 20	11.5	15	-118	-14	0.2	0.1	PE1V13005	$454.63	$431.90	$409.17	$390.98	4
50 - 100	DC - 20	12	15	-115	-12	0.05	0.1	PE1V13006	$454.63	$431.90	$409.17	$390.98	5
60 - 120	DC - 18.5	11	15	-114	-20	0.2	0.1	PE1V13007	$454.63	$431.90	$409.17	$390.98	6
75 - 150	DC - 18	11	15	-110	-20	0.2	0.4	PE1V13008	$454.63	$431.90	$409.17	$390.98	7
100 - 200	DC - 18	11	15	-113	-12	0.2	0.1	PE1V13009	$454.63	$431.90	$409.17	$390.98	8
150 - 300	DC - 20	11	15	-108	-14	1	2	PE1V13010	$454.63	$431.90	$409.17	$390.98	9
200 - 400	DC - 20	11	15	-106	-14	0.4	0.2	PE1V13011	$479.44	$455.47	$431.50	$412.32	10
400 - 800	DC - 9	8	5	-96	-14	3	1.3	PE1V13012	$454.63	$431.90	$409.17	$390.98	11
1,200 - 1,800	DC - 20	11	15	-89	-12	0.5	3	PE1V13013	$454.63	$431.90	$409.17	$390.98	12
3,000 - 3,500	DC - 10	10	11	-81	-16	2.5	12	PE1V13014	$479.44	$455.47	$431.50	$412.32	13
3,700 - 4,350	DC - 7.5	4	8	-83	-25	6	15	PE1V13015	$479.44	$455.47	$431.50	$412.32	14

Connectorized Packaged VCO w/ Field Replaceable Connectors

Coaxial Packaged Commercial Standard

Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1-9	10-24	25-49	50+	ROW
18 - 30	0.5 - 12	12	12	-120	-13	0.03	0.07	PE1V31000	$395.59	$375.81	$356.03	$340.21	15
25 - 50	0.5 - 15	11.5	15	-120	-12	0.05	0.03	PE1V31001	$424.09	$402.89	$381.68	$364.72	16
30 - 60	0.5 - 15	11	15	-119	-14	0.05	0.05	PE1V31002	$424.09	$402.89	$381.68	$364.72	17
40 - 80	0.5 - 20	12	15	-117	-14	0.05	0.05	PE1V31003	$424.09	$402.89	$381.68	$364.72	18
40 - 100	0.5 - 20	11.5	15	-118	-14	0.2	0.1	PE1V31004	$408.17	$387.76	$367.35	$351.03	19
50 - 100	0.5 - 20	12	15	-115	-12	0.05	0.1	PE1V31005	$424.09	$402.89	$381.68	$364.72	20
75 - 150	0.5 - 18	11	15	-110	-20	0.2	0.4	PE1V31007	Call	Call	Call	Call	21
200 - 400	0.5 - 20	11	15	-106	-14	0.4	0.2	PE1V31009	Call	Call	Call	Call	22
400 - 800	0.5 - 13	12	10	-94	-20	0.6	0.7	PE1V31010	Call	Call	Call	Call	23

* Phase Noise measured at 10 KHz offset frequency

Coaxial Packaged Commercial Standard

Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1-9	10-24	25-49	50+	ROW
1,200 - 1,800	0.5 - 20	11	15	-89	-12	0.5	3	PE1V31011	Call	Call	Call	Call	24
230 - 290	0.5 - 4.5	2	12	-107	-8.5			PE1V31015	$518.30	$492.39	$466.47	$445.74	25
500 - 600	0.5 - 4.5	-2	12	-105	-20			PE1V31016	$518.30	$492.39	$466.47	$445.74	26
850 - 890	DC - 5	8	12	-99	-5		5	PE1V31018	$518.30	$492.39	$466.47	$445.74	27
900 - 960	0.5 - 4	5.5	12	-110	-15		5	PE1V31019	$518.30	$492.39	$466.47	$445.74	28
1,700 - 1,850	0.5 - 4.5	0	12	-96	-15		13	PE1V31023	$518.30	$492.39	$466.47	$445.74	29
2,300 - 2,450	0.5 - 4.5	3	12	-101	-15		2	PE1V31025	$518.30	$492.39	$466.47	$445.74	30
2,400 - 2,800	1 - 11	9	12	-92	-10		50	PE1V31026	$518.30	$492.39	$466.47	$445.74	31
3,200 - 3,400	0.5 - 4.5	5	12	-88	-15		25	PE1V31027	$518.30	$492.39	$466.47	$445.74	32
1,435 - 1,650	0.5 - 5	7	12	-90	-7		35	PE1V31021	$518.30	$492.39	$466.47	$445.74	33
1,550 - 1,850	0.25 - 4.75	1.5	12	-99	-20		2	PE1V31022	$518.30	$492.39	$466.47	$445.74	34
620 - 660	0.5 - 4.5	0	12	-110	-13		2	PE1V31017	$518.30	$492.39	$466.47	$445.74	35
1,070 - 1,210	0.5 - 4.5	1.5	12	-109	-16		1	PE1V31020	$518.30	$492.39	$466.47	$445.74	36
2,165 - 2,360	0.5 - 10	5	12	-99	-10		10	PE1V31024	$518.30	$492.39	$466.47	$445.74	37
4,245 - 4,335	0.5 - 8	0.5	12	-87	-13		10	PE1V31028	$518.30	$492.39	$466.47	$445.74	38
5,220 - 5,420	0.5 - 4.5	-1	12	-83	-25		10	PE1V31029	$518.30	$492.39	$466.47	$445.74	39

Hi-REL Hermetic Buffer Amp

Frequency (MHz.)	Tuning Voltage (Vdc)	Output Power Typ (dBm)	Supply Voltage (Vdc)	Phase Noise* (dBc/Hz)	2nd Harmonics Typ (dBc)	Pushing Typ (MHz.)	Pulling Typ (MHz.)	Model No	1	2-4	5-9	10+	ROW
4,000 - 8,000	DC - 18	20	12	-75	-10	0.2	1	PE1V34000	$5,282.63	$5,097.74	$4,912.85	$4,754.37	40
5,000 - 10,000	DC - 20	20	12	-64	-15	0.2	1	PE1V34001	$6,095.16	$5,851.35	$5,607.55	$5,363.74	41
38,400 - 43,200	DC - 13	13	5	-74	-30	40	0.01	PE1V34003	$10,620.59	$10,195.77	$9,770.94	$9,346.12	42

Reference Oscillators

Loop Type	Out Freq (MHz)	Ref. Type	Out Power Typ (dBm)	2nd Harmonics Typ (dBc)	Spurious Typ (dBc)	Ph Noise @100kHz Offset (dBc/Hz)	Package Type	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
Free Running	10	Internal	+7	-20	-70	-145	Surface Mount	PE19XR1000	$412.99		See Web for Volume Pricing		43
				-25		-150	Connectorized	PE19XR1003	$2,128.44				44
	50			-20			Surface Mount	PE19XR1001	$427.19				45
				-25			Connectorized	PE19XR1004	$2,173.29				46
	100			-20		-155	Surface Mount	PE19XR1002	$501.18				47
				-25		-150	Connectorized	PE19XR1005	$2,338.84				48

TCXO Oscillators

CMOS

Output Freq. (GHz)	High Level Out Voltage (V min)	Low Level Out Voltage (V max)	Temp Stability (+/- ppm)	Ph Noise @10kHz Offset (dBc/Hz)	Dimensions (in)	Model No	1-4	5-9	10-24	25+	ROW
10	4.9	0.1	2.5	-145	1.25x1.25x 0.563	PE19XL6000	$769.03	$730.58	$692.13	$661.37	49
20						PE19XL6001	$729.25	$692.79	$656.33	$627.16	50

Phase Locked Oscillators



Loop Type	Out Freq (MHz)	Ref. Type	Ref. Input Freq. (MHz.)	Out Power Typ (dBm)	2nd Harmonics Typ (dBc)	Spurious Typ (dBc)	Package Type	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
Phase Locked	500	External	10	7	-35	-70	Connectorized	PE19XC7000	$1,690.59	See Web for Volume Pricing			51
					-25		Surface Mount	PE19XP5004	$475.25				52
			100				Connectorized	PE19XC7005	$1,603.12				53
							Surface Mount	PE19XP5009	$475.25				54
	1000		10				Connectorized	PE19XC7001	$1,690.59				55
							Surface Mount	PE19XP5005	$475.25				56
			100				Connectorized	PE19XC7006	$1,627.12				57
							Surface Mount	PE19XP5010	$475.25				58
	2000		10				Connectorized	PE19XC7002	$1,936.29				59
							Surface Mount	PE19XP5006	$676.17				60
			100				Connectorized	PE19XC7007	$1,936.29				61
							Surface Mount	PE19XP5011	$641.19				62
	4000		10		-35		Connectorized	PE19XC7003	$2,218.56				63
					-25		Surface Mount	PE19XP5007	$741.09				64
			100				Connectorized	PE19XC7008	$2,103.78				65
							Surface Mount	PE19XP5012	$702.73				66
	6000		10				Connectorized	PE19XC7004	$2,411.20				67
							Surface Mount	PE19XP5008	$771.95				68
			100				Connectorized	PE19XC7009	$2,411.20				69
							Surface Mount	PE19XP5013	$771.95				70

Phase Locked Crystal Oscillators

Loop Type	Out Freq (MHz)	Ref. Type	Ref. Input Freq. (MHz)	Out Power Typ (dBm)	2nd Harmonics Typ (dBc)	Spurious Typ (dBc)	Package Type	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
Phase-Locked Crystal	50	External	10	+7	-20	-70	Surface Mount	PE19XP5000	$720.05	See Web for Volume Pricing			71
							Connectorized	PE19XP5002	$2,615.93				72
	100						Surface Mount	PE19XP5001	$864.74				73
							Connectorized	PE19XP5003	$2,872.10				74

TAPPERS

Equal Split

Frequency Range (MHz.)	Number of Ports	Maximum Power	Directivity (dB)	Model No	1-9	10-24	25-49	50+	ROW
376-2,200		500 Watt		PE-T1009	$229.32	$217.85	$206.39	$197.22	75
380-2,500				PE-T1000	$214.26	$205.69	$199.26	$194.98	76
600-2,700		300 Watt		PE20DV1026	$224.03	$212.83	$201.63	$192.67	77
				PE20DV1027	$284.23	$270.02	$255.81	$244.44	78
				PE20DV1028	$253.92	$241.22	$228.53	$218.37	79
				PE20DV1029	$322.88	$306.74	$290.59	$277.68	80
				PE20DV1030	$276.32	$262.50	$248.69	$237.64	81
				PE20DV1031	$336.05	$319.25	$302.45	$289.00	82
				PE-T1012	$214.26	$205.69	$199.26	$194.98	83
700-2,700		500 Watt		PE-T1003	$192.49	$182.87	$173.24	$165.54	84
				PE-T1010	$220.07	$209.07	$198.06	$189.26	85

Unequal Split

Frequency Range (MHz.)	Coupling (dB)	Maximum Power	Directivity (dB)	Model No	1-9	10-24	25-49	50+	ROW
350-5,850	5	300 Watt	2	PETP1001	$261.37	$248.30	$235.23	$224.78	86
	6		3	PETP1002	$216.56	$205.73	$194.90	$186.24	87
				PETP1003	$261.37	$248.30	$235.23	$224.78	88
	7		4	PE-T2006	$190.57	$182.95	$177.23	$173.42	89
				PETP1004	$228.39	$216.97	$205.55	$196.42	90
				PETP1005	$261.37	$248.30	$235.23	$224.78	91
	8		5	PE-T2003	$190.57	$182.95	$177.23	$173.42	92
				PETP1006	$216.56	$205.73	$194.90	$186.24	93
				PETP1007	$261.37	$248.30	$235.23	$224.78	94
	9		7	PETP1008	$216.56	$205.73	$194.90	$186.24	95
				PETP1009	$265.28	$252.02	$238.75	$228.14	96
	10		9	PE-T2007	$277.49	$263.62	$249.74	$238.64	97
				PETP1010	$216.56	$205.73	$194.90	$186.24	98
	13		19	PE-T2018	$165.16	$156.90	$148.64	$142.04	99
	15		30	PE-T2001	$183.41	$176.07	$170.57	$166.90	1
				PE-T2015	$190.75	$183.12	$177.40	$173.58	2
				PETP1012	$216.56	$205.73	$194.90	$186.24	3
				PETP1013	$261.37	$248.30	$235.23	$224.78	4
	20		100	PE-T2000	$180.70	$173.47	$168.05	$164.44	5
				PETP1014	$216.56	$205.73	$194.90	$186.24	6
				PETP1015	$261.37	$248.30	$235.23	$224.78	7
	30		1000	PE-T2004	$180.70	$173.47	$168.05	$164.44	8
				PETP1016	$216.56	$205.73	$194.90	$186.24	9
				PETP1017	$261.37	$248.30	$235.23	$224.78	10
380-6,000	6		3	PE-T2014	$165.16	$156.90	$148.64	$142.04	11
	7		4	PE-T2011	$165.16	$156.90	$148.64	$142.04	12
	8		5	PE-T2012	$165.16	$156.90	$148.64	$142.04	13
	9		7	PE-T2010	$165.16	$156.90	$148.64	$142.04	14
	11		12	PE-T2025	$165.16	$156.90	$148.64	$142.04	15
	20		100	PE-T2017	$233.49	$221.82	$210.14	$200.80	16
698-2,700	10		9	PE-T2016A	$244.64	$232.41	$220.18	$210.39	17
	30		1000	PE-T2023	$257.99	$245.09	$232.19	$221.87	18
700-2,700	5		2	PE-T2013	$209.75	$199.26	$188.78	$180.39	19

INDEX GUIDE TO
TERMINATIONS AND MATCHING PADS

TERMINATIONS AND MATCHING PADS.....342

MATCHING PADS.....347

Matching pads designed to mate with 50 ohm connectors on one end and 75 ohm connectors on the opposite end are available in a range of connector options.

Resistive Impedance Transformers.....347

TERMINATIONS.....343

RF Coaxial Terminations are available in a number of connector options and frequency ranges. Power ratings for these terminations range from 1/2 watt to 500 watts of continuous power. 50 ohm and 75 ohm options are available as well.

RF Load.....343 | Feed-Thru Load.....347

TERMINATIONS

RF Load

50 Ohm

Max. Power (Watts)	Connector	Maximum Frequency.	Construction Material	VSWR Max.	Chain	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
0.25 W	Mini SMP Female	18 GHz	Gold Plated Beryllium Copper	1.35:1	No	PE6184	$55.38		See Web for Volume Pricing		1
		40 GHz		1.45:1	No	PE6182	$161.58				2
0.5 W	2.92mm Male	40 GHz	Passivated Stainless Steel	1.2:1	Yes	PE6086	$415.02				3
					No	PE6085	$298.64				4
	2.92mm Female				Yes	PE6088	$454.25				5
					No	PE6087	$454.69				6
	7/16 DIN Male	1,000 MHz	Tri-Metal Plated Brass		No	PE6146	$135.55				7
	Mini SMP Male	40 GHz	Gold Plated Beryllium Copper	1.35:1	No	PE6163	$262.55				8
	Mini SMP Female		Gold over Nickel Plated Beryllium Copper		No	PE6162	$298.48				9
	SMA Male	12.4 GHz	Passivated Stainless Steel	1.17:1	No	PE6002	$40.56				10
	SMA Female				Yes	PE6070	$88.71				11
	SMP Female	18 GHz	Gold Plated Beryllium Copper	1.35:1	No	PE6183	$40.62				12
		26.5 GHz		1.3:1	No	PE6181	$109.47				13
1 W	1.85mm Male	65 GHz	Passivated Stainless Steel	1.6:1	Yes	PE6236	$613.86				14
					No	PE6235	$539.79				15
		67 GHz			Yes	PE6TR1101	$400.67				16
					No	PE6TR1100	$380.07				17
	1.85mm Female				No	PE6TR1102	$380.07				18
	2.4mm Male	50 GHz	Passivated Stainless Steel	1.45:1	Yes	PE6179	$577.87				19
				1.2:1	Yes	PE6TR1104	$390.37				20
			Passivated Stainless Steel	1.45:1	No	PE6178	$522.30				21
				1.2:1	No	PE6TR1103	$380.07				22
	2.4mm Female				No	PE6TR1105	$380.07				23
	2.92mm Male	40 GHz	Passivated Stainless Steel	1.25:1	Yes	PE6174	$313.17				24
				1.15:1	Yes	PE6TR1107	$256.47				25
			Passivated Stainless Steel	1.25:1	No	PE6173	$276.03				26
				1.15:1	No	PE6TR1106	$246.17				27
	2.92mm Female		Passivated Stainless Steel	1.25:1	No	PE6175	$347.20				28
				1.15:1	No	PE6TR1108	$266.77				29
	3.5mm Male	34.5 GHz			No	PE6TR1109	$277.07				30
				1.25:1	No	PE6TR1110	$256.47				31
	3.5mm Female			1.15:1	No	PE6TR1111	$277.07				32
				1.25:1	No	PE6TR1112	$256.47				33
	BMA Plug	18 GHz		1.2:1		PE6TR1041	$178.08				34
	BMA Jack			1.3:1		PE6TR1042	$191.26				35
	Mini SMP Female			1.2:1		PE6TR1044	$58.73				36
				1.15:1	No	PE6TR1117	$55.52				37
		27 GHz		1.2:1	No	PE6TR1118	$101.97				38
		40 GHz			No	PE6TR1119	$163.77				39
		50 GHz		1.4:1	No	PE6TR1120	$256.47				40
	MMCX Male	6 GHz	Gold Plated Brass	1.35:1	No	PE6199	$29.83				41
	QMA Male	4 GHz		1.2:1		PE6TR1050	$16.64				42
					Yes	PE6TR1051	$23.53				43
	QN Male					PE6TR1038	$53.05				44
	SMA Male		Gold Plated Brass	1.1:1	No	PE6150	$7.10				45
		6 GHz	Tri-Metal Plated Brass	1.2:1	No	PE6241	$16.16				46
					No	PE6TR1014	$9.32				47
		18 GHz	Passivated Stainless Steel		Yes	PE6069	$64.72				48
				1.25:1	Yes	PE6072	$96.45				49
					No	PE6071	$59.07				50
		26.5 GHz		1.35:1	Yes	PE6078	$119.95				51
					No	PE6077	$119.17				52
	SMA Female	18 GHz		1.25:1	No	PE6073	$93.71				53
		26.5 GHz		1.35:1	Yes	PE6080	$172.87				54
					No	PE6079	$143.54				55
	SMB Plug	4 GHz	Gold Plated Brass	1.2:1	No	PE6TR1037	$26.55				56
	SMB Jack				No	PE6TR002	$12.36				57
	SMC Jack	10 GHz		1.35:1	No	PE6TR005	$9.97				58

RF Load

50 Ohm

Max. Power (Watts)	Connector	Maximum Frequency.	Construction Material	VSWR Max.	Chain	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
1 W	SMP Male	18 GHz		1.2:1		PE6TR1039	$124.63		See Web for Volume Pricing		59
			Gold over Nickel Plated Brass		No	PE6161	$225.86				60
	SMP Female			1.2:1		PE6TR1040	$58.73				61
			Gold Plated Brass		No	PE6160	$173.76				62
				1.15:1	No	PE6TR1113	$50.47				63
		27 GHz		1.2:1	No	PE6TR1114	$112.27				64
		40 GHz			No	PE6TR1115	$163.77				65
				1.3:1	No	PE6TR1116	$153.47				66
	SSMC Plug	10 GHz	Gold Plated Brass		No	PE6243	$28.45				67
2 W	2.4mm Male	50 GHz	Passivated Stainless Steel	1.45:1	No	PE6227	$338.91				68
					No	PE6242	$549.20				69
	2.4mm Female				No	PE6180	$610.10				70
	2.92mm Male	40 GHz		1.25:1	Yes	PE6177	$421.20				71
					No	PE6176	$371.36				72
	4.3-10 Male	6 GHz		1.15:1		PE6TR1045	$49.26				73
					Yes	PE6TR1046	$46.52				74
						PE6TR1047	$53.67				75
					Yes	PE6TR1048	$54.69				76
	7/16 DIN Male	3 GHz	Silver Plated Brass	1.1:1		PE6190	$69.64				77
			Aluminum			PE6TR1013	$72.40				78
		6 GHz	Tri-Metal Plated Brass	1.2:1	No	PE6196	$38.00				79
	BNC Male	3 GHz		1.15:1	No	PE6TR007	$23.15				80
		4 GHz			Yes	PE6TR008	$25.60				81
			Nickel Plated Brass		No	PE6156	$28.27				82
				1.2:1	No	PE6TR010	$28.44				83
	N Male		Nickel Plated Brass	1.1:1	No	PE6154	$39.92				84
		6 GHz	Tri-Metal Plated Brass	1.2:1	No	PE6248	$29.60				85
					No	PE6249	$20.95				86
				1.2:1	No	PE6TR009	$19.62				87
				1.3:1	No	PE6TR012	$24.61				88
		18 GHz	Nickel Plated Brass		Yes	PE6075	$94.56				89
					No	PE6009	$58.59				90
	N Female	6 GHz	Tri-Metal Plated Brass	1.2:1	No	PE6TR011	$27.94				91
		18 GHz	Nickel Plated Brass		Yes	PE6076	$153.34				92
				1.3:1	No	PE6032	$85.98				93
	QMA Male	3 GHz		1.1:1		PE6TR1052	$16.97				94
		6 GHz		1.15:1	No	PE6TR1036	$37.91				95
	SMA Male	18 GHz	Passivated Stainless Steel	1.3:1	Yes	PE6082	$78.42				96
					No	PE6081	$57.98				97
		26.5 GHz	Gold Plated Stainless Steel	1.35:1	Yes	PE6TR675	$97.14				98
			Passivated Stainless Steel		Yes	PE6TR677	$93.51				99
			Gold Plated Stainless Steel		No	PE6TR671	$76.50				1
			Passivated Stainless Steel		No	PE6TR673	$87.97				2
	SMA Female	18 GHz		1.3:1	Yes	PE6084	$107.54				3
					No	PE6083	$78.33				4
	TNC Male	6 GHz	Tri-Metal Plated Brass	1.2:1	Yes	PE6TR014	$19.99				5
					No	PE6172	$20.57				6
				1.35:1	No	PE6TR016	$14.76				7
		18 GHz	Passivated Stainless Steel	1.25:1	Yes	PE6090	$143.94				8
					No	PE6089	$136.24				9
	TNC Female	6 GHz	Tri-Metal Plated Brass		No	PE6229	$32.54				10
				1.3:1	No	PE6TR015	$26.50				11
		18 GHz	Passivated Stainless Steel	1.25:1	Yes	PE6092	$229.54				12
					No	PE6091	$159.83				13
5 W	2.92mm Male	40 GHz	Black Anodized Aluminum Heatsink	1.35:1	No	PE6TR028	$787.06				14
	7/16 DIN Male	7 GHz	Tri-Metal Plated Brass	1.25:1	No	PE6100	$224.77				15

RF Load

50 Ohm

Max. Power (Watts)	Connector	Maximum Frequency.	Construction Material	VSWR Max.	Chain	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
5 W	7/16 DIN Female	7 GHz	Tri-Metal Plated Brass		No	PE6139	$223.45		See Web for Volume Pricing		16
	N Male	3 GHz	Aluminum	1.15:1		PE6187	$39.35				17
		6 GHz		1.25:1		PE6186	$87.43				18
		18 GHz	Black Anodized Aluminum Heatsink		No	PE6097	$151.33				19
	N Female				No	PE6098	$183.62				20
	SMA Male				No	PE6095	$128.43				21
	SMA Female				No	PE6096	$196.97				22
	TNC Male				No	PE6099	$186.39				23
	TNC Female				No	PE6138	$212.97				24
10 W	7/16 DIN Male	7 GHz	Black Anodized Aluminum Heatsink	1.25:1	No	PE6105	$349.93				25
	7/16 DIN Female				No	PE6141	$338.93				26
	BNC Male	4 GHz			No	PE6034	$187.63				27
	BNC Female				No	PE6101	$251.38				28
	N Male	6 GHz		1.15:1	No	PE6185	$119.10				29
		18 GHz		1.4:1	No	PE6035	$273.05				30
	N Female				No	PE6102	$307.09				31
	SMA Male				No	PE6036	$211.22				32
	SMA Female				No	PE6103	$283.90				33
	TNC Male				No	PE6104	$284.27				34
	TNC Female				No	PE6140	$358.97				35
20 W	4.1/9.5 Mini DIN Male	2.7 GHz	Black Anodized Aluminum	1.33:1		PE6TR1022	$471.59				36
	4.3-10 Male					PE6TR1023	$490.46				37
	7/16 DIN Male					PE6TR1021	$429.31				38
	N Male					PE6TR1020	$446.06				39
25 W	7/16 DIN Male	7 GHz	Black Anodized Aluminum Heatsink	1.25:1	No	PE6107	$465.01				40
		8 GHz		1.6:1		PE6209	$344.24				41
	7/16 DIN Female					PE6210	$344.24				42
	N Male	3 GHz		1.2:1	No	PE6228	$146.40				43
		18 GHz		1.6:1		PE6205	$462.78				44
				1.4:1	No	PE6106	$497.23				45
	N Female			1.6:1		PE6206	$448.31				46
				1.4:1	No	PE6037	$595.46				47
	SMA Male			1.6:1		PE6203	$456.61				48
	SMA Female					PE6204	$409.65				49
				1.4:1	No	PE6038	$538.77				50
	TNC Male			1.6:1		PE6207	$490.32				51
	TNC Female					PE6208	$446.25				52
30 W	SMA Female	4.2 GHz	Chem Film Plated Aluminum	1.25:1		PE6TR1000	$212.13				53
40 W	4.1/9.5 Mini DIN Male	2.7 GHz	Black Anodized Aluminum	1.15:1		PE6TR1026	$656.45				54
	4.3-10 Male					PE6TR1027	$670.05				55
	7/16 DIN Male					PE6TR1025	$500.85				56
	N Male					PE6TR1024	$500.85				57
50 W	7/16 DIN Male	2.7 GHz	Aluminum	1.2:1	No	PE6238	$821.68				58
		3 GHz	Black Anodized Aluminum Heatsink	1.15:1		PE6191	$379.66				59
		4 GHz		1.25:1	No	PE6169	$510.98				60
		8 GHz		1.6:1		PE6217	$529.20				61
	7/16 DIN Female					PE6218	$605.39				62
	N Male	3 GHz		1.1:1		PE6189	$254.29				63
		4 GHz		1.2:1		PE6188	$371.67				64
		8.5 GHz		1.3:1	No	PE6TR029	$303.37				65
		18 GHz		1.6:1		PE6213	$533.35				66
				1.45:1	No	PE6198	$463.73				67
	N Female	3 GHz	Aluminum	1.25:1		PE6233	$291.41				68
		18 GHz	Black Anodized Aluminum Heatsink	1.1:1		PE6234	$202.14				69
				1.6:1		PE6214	$525.58				70
				1.45:1	No	PE6039	$642.93				71
	SMA Male			1.6:1		PE6211	$541.14				72
	SMA Female	3 GHz	Nickel Plated Brass	1.25:1		PE6232	$219.12				73

RF Load

50 Ohm

Max. Power (Watts)	Connector	Maximum Frequency.	Construction Material	VSWR Max.	Chain	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
50 W	SMA Female	6 GHz	Chem Film Plated Aluminum	1.25:1		PE6TR1001	$439.78		See Web for Volume Pricing		74
		18 GHz	Black Anodized Aluminum Heatsink	1.6:1		PE6212	$511.02				75
				1.45:1	No	PE6040	$716.94				76
	TNC Male			1.6:1		PE6215	$497.63				77
	TNC Female					PE6216	$539.99				78
60 W	4.1/9.5 Mini DIN Male	2.7 GHz	Black Anodized Aluminum	1.15:1		PE6TR1030	$572.41				79
	4.3-10 Male					PE6TR1031A	$708.36				80
	7/16 DIN Male					PE6TR1029	$691.38				81
	N Male					PE6TR1028	$554.52				82
100 W	4.3-10 Male	2.7 GHz	Black Anodized Aluminum			PE6TR1035A	$943.18				83
	4.3-10 Female					PE6TR1035F	$943.18				84
	7/16 DIN Male					PE6TR1033A	$804.95				85
		3 GHz	Black Anodized Aluminum Heatsink	1.2:1	No	PE6197	$374.98				86
	7/16 DIN Female	2 GHz		1.35:1	No	PE6137	$940.98				87
		2.7 GHz	Black Anodized Aluminum			PE6TR1033F	$804.95				88
			Aluminum	1.2:1	No	PE6239	$1,173.82				89
	BNC Female	2 GHz	Black Anodized Aluminum Heatsink		No	PE6041	$924.98				90
	N Male	2.7 GHz	Black Anodized Aluminum			PE6TR1032A	$804.95				91
		4 GHz	Black Anodized Aluminum Heatsink		No	PE6168	$571.23				92
	N Female	2.7 GHz	Black Anodized Aluminum			PE6TR1032F	$848.87				93
		8 GHz	Black Anodized Aluminum Heatsink	1.5:1		PE6222	$721.25				94
	SMA Male					PE6219	$759.32				95
	SMA Female	2 GHz		1.3:1	No	PE6043	$976.50				96
		6 GHz	Chem Film Plated Aluminum	1.25:1		PE6TR1002	$449.99				97
		8 GHz	Black Anodized Aluminum Heatsink	1.5:1		PE6220	$677.96				98
	TNC Female					PE6224	$517.64				99
150 W	SMA Female	3 GHz	Chem Film Plated Aluminum	1.3:1		PE6TR1003	$442.61				1
200 W	N Male	3 GHz	Black Anodized Aluminum Heatsink	1.25:1	No	PE6230	$619.78				2
	N Female					PE6231	$639.15				3
300 W	N Female	3 GHz	Chem Film Plated Aluminum	1.3:1		PE6TR1004	$570.99				4
500 W	N Female	1.2 GHz	Chem Film Plated Aluminum	1.25:1		PE6TR1005	$555.88				5
800 W	N Female	500 MHz	Chem Film Plated Aluminum	1.5:1		PE6TR1006	$702.88				6

75 Ohm

Max. Power (Watts)	Connector	Maximum Frequency.	Construction Material	VSWR Max.	Chain	Model No	1-24	25-49	50-99	100+	ROW
0.25 W	F Male	3 GHz	Nickel Plated Zinc			PE6202-100PK	$76.04	$72.24	$68.44	$65.39	7
						PE6202-25PK	$22.09	$20.99	$19.88	$19.00	8
					No	PE6202	$1.28	$1.22	$1.15	$1.10	9
1 W	BNC Male	1,000 MHz	Nickel Plated Brass		No	PE6165	$17.31	$16.44	$15.58	$14.89	10
		2 GHz	Tri-Metal Plated Brass	1.35:1	No	PE6TR004	$64.61	$61.38	$58.15	$55.56	11
2 W	BNC Male	2 GHz		1.2:1	No	PE6TR040	$19.55	$18.57	$17.60	$16.81	12
	BNC Female			1.15:1	No	PE6TR003	$65.84	$62.55	$59.26	$56.62	13

Feed-Thru Load

50 Ohm

Max. Power (Watts)	Connector Input	Connector Output	Maximum Frequency.	Construction Material	VSWR Max.	Chain	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
2 W	BNC Male	BNC Female	1,000 MHz	Tri-Metal Plated Brass	1.3:1	No	PE6TR000	$52.48		See Web for Volume Pricing		14
	N Male	N Female		Nickel Plated Brass	1.65:1	No	PE6033	$153.34				15
	SMA Male	SMA Female		Passivated Stainless Steel	1.25:1	No	PE6026	$91.81				16

75 Ohm

Max. Power (Watts)	Connector Input	Connector Output	Maximum Frequency.	Construction Material	VSWR Max.	Chain	Model No	1-24	25-49	50-99	100+	ROW
2 W	BNC Male	BNC Female	1,000 MHz	Tri-Metal Plated Brass	1.3:1	No	PE6TR001	$37.24	$35.38	$33.52	$32.03	17

Resistive Impedance Transformers

Model No	Connector A 50 Ω	Connector B 75 Ω	Max. Frequency (MHz.)	VSWR Max.	Attenuation Loss (dB)	Accuracy (dB)	1 Pc. Price	See Web for Volume Pricing			ROW
PE7006	BNC Male	BNC Female	2,000	1.2:1		±0.5	$65.80		See Web for Volume Pricing		18
PE7007	BNC Male	BNC Female	2,000	1.2:1	6		$62.84				19
PE7067	BNC Male	F Male	3,000	1.25:1	5.7	±0.5	$129.49				20
PE7066	BNC Male	F Female	3,000	1.25:1		±0.5	$147.15				21
PE7068	BNC Female	F Male	3,000	1.25:1		±0.5	$140.35				22
PE7072	N Male	F Male	3,000	1.25:1		±0.5	$151.12				23
PE70MP1002	N Male	F Female	3,000				$131.27				24
PE7071	N Male	F Female	3,000	1.25:1		±0.5	$113.68				25
PE7027	N Male	N Female	2,000	1.2:1		±0.5	$129.26				26
PE7070	N Male	N Female	3,000	1.35:1		±0.5	$129.69				27
PE7073	N Female	F Male	3,000	1.25:1		±0.5	$190.64				28
PE70MP1001	N Female	F Female	3,000				$169.34				29
PE7074	N Female	F Female	3,000	1.25:1		±0.5	$155.34				30
PE7028	N Female	N Male	500	1.35:1		±0.5	$29.40				31
PE7083	N Female	N Male	3,000	1.35:1		±0.5	$169.68				32
PE70MP1007	SMA Male	F Male	3,000				$106.82				33
PE7075	SMA Male	F Male	3,000	1.25:1		±0.5	$162.56				34
PE70MP1006	SMA Male	F Female	3,000				$116.09				35
PE7076	SMA Male	F Female	3,000	1.25:1		±0.5	$118.60				36
PE70MP1005	SMA Female	F Male	3,000				$106.82				37
PE7077	SMA Female	F Male	3,000	1.25:1		±0.5	$107.70				38
PE70MP1004	SMA Female	F Female	3,000				$126.74				39
PE7078	SMA Female	F Female	3,000	1.25:1		±0.5	$129.50				40
PE7079	TNC Male	F Female	3,000	1.25:1	5.7	±0.5	$169.34				41
PE7081	TNC Female	F Male	3,000	1.25:1	5.7	±0.5	$171.89				42
PE7082	TNC Female	F Female	3,000	1.25:1	5.7	±0.5	$117.84				43

INDEX GUIDE TO
TEST AND MESUREMENT PRODUCTS

TEST AND MEASUREMENT PRODUCTS.....348

1.0MM FLEXIBLE VNA 110 GHZ PRECISION CABLES.....352

26.5 GHZ & 40 GHZ TEST CABLES.....354

4 - IN - 1 CALIBRATION KITS.....349

40 GHZ SKEW MATCHED CABLES.....350

50 GHZ & 67 GHZ TEST CABLE ASSEMBLIES.....351

75 OHM TEST CABLE ASSEMBLIES.....354

CALIBRATION KITS.....348

COAXIAL RF PROBES & PROBE POSITIONING HARDWARE.....349

HANDHELD RF ANALYZER RUGGED PHASE STABLE CABLE ASSEMBLIES.....350

PE-TC151 SERIES PHASE STABLE TEST CABLE ASSEMBLIES.....353

PE-TC195 SERIES PHASE STABLE TEST CABLE ASSEMBLIES.....353

RUGGEDIZED VNA CABLE ASSEMBLIES.....351

SEMI-RIGID PIGTAIL TEST PROBES.....354

VNA TEST CABLES.....349

CALIBRATION KITS

Bench Type Calibration Kits

Connector Series	Impedance (Ohms)	Frequency Range (GHz)	Cal Type	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
2.4mm	50	DC to 50	SOL	PE5CK1015	$8,549.00	See Web for Volume Pricing			1
			SOLT	PE5CK1016	$11,514.07				2
2.92mm		DC to 40	SOL	PE5CK1017	$12,346.61				3
			SOLT	PE5CK1018	$14,372.11				4
3.5mm		DC to 8.5		PE5CK1001	$3,633.44				5
		DC to 26.5	SOL	PE5500-KIT	$4,546.17				6
			SOLT	PE5CK1000	$5,484.45				7
			SOL	PE5CK1019	$6,995.76				8
			SOLT	PE5CK1020	$7,743.11				9
7/16 DIN		DC to 7.5	SOL	PE5CK1021	$9,358.71				10
			SOLT	PE5CK1022	$13,820.83				11
7mm		DC to 18	SOL	PE5CK1023	$6,463.91				12
BNC		DC to 10		PE5CK1024	$7,772.78				13
N		DC to 18	SOLT	PE5501-KIT	$5,910.34				14
			SOL	PE5CK1025	$5,353.49				15
				PE5CK1026	$7,342.75				16
F	75	DC to 3	SOLT	PE5CK1002	$2,716.35				17
				PE70MP5000	$4,700.78				18

Test & Measurement

VNA TEST CABLES

For Use With Interchangeable Connectors

Impedance (Ohms)	Connector Series	Frequency Range (GHz)	Type	Model No	1	2-4	5-9	10+	ROW
50	3.5mm NMD Female	DC - 26.5	Cable for Interchangeable Connectors	PE310-KIT	$5,550.61	$5,356.34	$5,162.07	$4,995.55	19

Interchangeable Connectors

Impedance (Ohms)	Connector Series	Frequency Range (GHz)	Gender	Polarity	Type	Model No	1 Pc. Price	See Web for Volume Pricing		ROW
50	3.5mm	DC - 26.5	Female	Standard	Connector	PE44488	$661.67	See Web for Volume Pricing		20
			Male			PE44487	$696.53			21
	N	DC - 18	Female			PE44486	$417.48			22
			Male			PE44485	$467.49			23

4 - IN - 1 CALIBRATION KITS

Product Features

- Lightweight Portable 4-in-1 Package
- Precision 3.5mm Connectors
- Gold Plated Short Open Load Thru
- Supports 26.5 GHz SOLT Calibration
- Calibration Coefficients on Data Sheet

Connector 1	Impedance (Ohms)	Freq. Range (GHz)	Weight (lbs.)	Model No	1	2-4	5-9	10+	ROW
3.5mm Female Short Open Load Thru	50	DC to 26.5	2.752	PE5CK1012	$4,067.45	$3,904.75	$3,742.05	$3,579.36	24
3.5mm Male Short Open Load Thru				PE5CK1013	$4,120.52	$3,955.70	$3,790.88	$3,626.06	25

COAXIAL RF PROBES & PROBE POSITIONING HARDWARE

Product Features

PCB RF Probe Positioner (PE5TL1000): $1,269.78

- RF PCB probe positioner holds coaxial probes
- Magnetic mounting plate
- On-Off positioner switch
- Articulated joints
- Multi-axis positioner control

Coaxial RF Microwave GS and GSG Probe Series (PE2PB1000-PE2PB1003):

- Max. Operating Frequency of 20 GHz
- RF probe Return Loss better than 10 dB
- GS and GSG Probes Feature Gold Plated Contacts
- Compliant coaxial GSG (or GS) pogo pins

RF MICROWAVE PROBES

Probe Tip Config.	Number of Ground	Pitch 1 (µm)	Pitch 2 (µm)	Connector 1	Imp. (Ω)	Freq. Max (GHz)	RL Max (dB)	IL Max (dB)	Model No	1-4	5-9	10-24	25+	ROW
GS	1	800		2.92mm Female	50	40	10	0.5	PE2PB1006	$882.24	$838.13	$794.02	$758.73	26
				3.5mm Female		20			PE2PB1002	$630.58	$599.05	$567.52	$542.30	27
	2	1500	2,500	2.92mm Female		40			PE2PB1007	$908.39	$862.97	$817.55	$781.22	28
				3.5mm Female		20			PE2PB1003	$649.28	$616.82	$584.35	$558.38	29
GSG		800		2.92mm Female		40			PE2PB1004	$947.81	$900.42	$853.03	$815.12	30
				3.5mm Female		20			PE2PB1000	$677.30	$643.44	$609.57	$582.48	31
	4	1500	2,500	2.92mm Female		40			PE2PB1005	$973.96	$925.26	$876.56	$837.61	32
				3.5mm Female		20			PE2PB1001	$695.99	$661.19	$626.39	$598.55	33

40 GHZ SKEW MATCHED CABLES

Product Features

- 1 ps Delay match
- Excellent VSWR of 1.4:1
- 100% tested up to 40 GHz
- Extremely Flexible
- Polarity indicators on cable ends

Connector 1	Connector 2	Max Frequency (GHz)	Max VSWR	Typ Insertion Loss (dB/ft)	Model No	1	2-4	5-9	10+	ROW
2.92mm Male	2.92mm Male	40	1.4:1	1.4	PE3C4680-12	$1,173.34	$1,126.41	$1,079.47	$1,032.54	34
				2.8	PE3C4680-24	$1,300.04	$1,248.04	$1,196.04	$1,144.04	35
				5.6	PE3C4680-48	$1,553.43	$1,491.29	$1,429.16	$1,367.02	36

HANDHELD RF ANALYZER RUGGED PHASE STABLE CABLE ASSEMBLIES

Product Features

- Designed for in-field measurements with handheld or portable analyzers
- Excellent VSWR as low as 1.2:1
- Excellent Phase Stability with Flexure as low as 1.5 degrees
- Rugged Armor provides 1200 p.s.i crush resistance plus torque resistance
- UV resistance jacket
- Each assembly is serialized and includes test data

Connector 1	Connector 2	Freq. Max (GHz)	Imp (Ohm)	VSWR	IL @fmax (dB/ft)	Phase Stability with Flexure (Degrees)	Length (in)	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
N Male	7/16 DIN Male	7	50	1.2:1	2.16	1.5	60.0	PE3C4000-60	$657.16		See Web for Volume Pricing		37
					4.92		144.0	PE3C4000-144	$861.72				
	7/16 DIN Female				2.16		60.0	PE3C4001-60	$928.81				38
					4.92		144.0	PE3C4001-144	$1,157.97				
	N Male	9			2.52		60.0	PE3C4002-60	$536.42				39
					5.74		144.0	PE3C4002-144	$791.30				
	N Male Right Angle				2.52		60.0	PE3C4003-60	$824.84				40
					5.74		144.0	PE3C4003-144	$1,136.07				
	N Female				2.52		60.0	PE3C4004-60	$536.42				41
					5.74		144.0	PE3C4004-144	$791.30				
	N Male	18		1.3:1	2.66	2.0	39.4	PE3C4005-100CM	$648.53				42
	N Male Right Angle							PE3C4006-100CM	$871.78				43
	N Female							PE3C4007-100CM	$690.69				44
	SMA Male				3.89		60.0	PE3C4008-60	$747.71				45
	SMA Female							PE3C4009-60	$747.71				46
	TNC Male							PE3C4010-60	$1,046.18				47
	TNC Female							PE3C4011-60	$1,046.18				48
3.5mm Male	3.5mm Female	27			3.46	4.0	39.4	PE3C4012-100CM	$945.57				49
3.5mm Female								PE3C4013-100CM	$945.57				50

RUGGEDIZED VNA TEST CABLE ASSEMBLIES

Product Features

- Rugged VNA test port extenders
- Torsion resistant connector heads
- Max phase variation +/- 2˚ with flexure to 18 GHz
- Max phase variation +/- 3˚ with flexure to 26.5 GHz
- Max phase variation +/- 5˚ with flexure to 40 GHz
- 5,000 mating cycles minimum
- 75,000 flexure cycles minimum
- Each cable is serialized and comes with RF test data
- SMA, Type-N, 2.92mm and 2.4mm configurations available

Pasternack's ruggedized VNA test cables are designed to provide customers with repeatable accurate VNA measurements. These test cables have excellent electrical properties including low insertion loss, low VSWR and phase stability of +/- 2˚ to 18 GHz with flexure. Torsion resistant connector heads are directly attached to stainless steel conduit style armoring providing a rugged design for up to 5,000 mating cycles with proper care. The cable armoring enhances amplitude and phase stability by preventing stress due to over bending while maintaining the flexibility required for testing in a lab environment. When used with the appropriate calibration kit these test cables effectively extend the test port of the VNA allowing for accurate measurements of devices that cannot be directly connected to a Network Analyzer test port.

Connector 1	Connector 2	Freq. Max (GHz)	Imp (Ohm)	VSWR	IL (dB/ft)	IL (dB/m)	Phase Stability with Flexure (Degrees)	Flex Cycles	Model No	1 Pc. Price	See Web for Volume Pricing		ROW
2.4mm Male	2.4mm Female	40	50	1.38:1	0.83	2.72	5	- - -	PE3VNA4005-24	$2,292.19		See Web for Volume Pricing	51
	2.4mm Male								PE3VNA4004-24	$2,138.38			52
2.92mm Male	2.92mm Female	26.5		1.25:1	0.64	2.1	3		PE3VNA2606-24	$1,649.29			53
		40		1.38:1	0.83	2.72	5		PE3VNA4002-24	$2,155.32			54
	2.92mm Male	26.5		1.25:1	0.64	2.1	3		PE3VNA2605-24	$1,616.99			55
		40		1.38:1	0.83	2.72	5		PE3VNA4001-24	$2,087.53			56
3.5mm Male	3.5mm Female	26.5		1.3:1	0.64	2.1	3		PE3VNA2604-24	$1,616.99			57
	3.5mm Male			1.25:1					PE3VNA2603-24	$1,584.74			58
N Male	N Female	18			0.52	1.71	2		PE3VNA1804-24	$874.60			59
	N Male								PE3VNA1803-24	$858.46			60
SMA Male	SMA Female								PE3VNA1802-24	$858.46			61
	SMA Male								PE3VNA1801-24	$842.31			62

See Web for other lengths

50 AND 67 GHZ TEST CABLE ASSEMBLIES

Product Features

- Highly flexible VNA test cables up to 50 and 67 GHz
- Max phase variation +/- 6˚ to 50 GHz and +/- 8˚ to 67 GHz with flexure
- VSWR of 1.3:1 to 50 GHz and 1.4:1 to 67 GHz
- Rated up to 5,000 mating cycles
- Up to 100,000 flex cycles
- Swept right angle connector options available
- Highly flexible stainless steel braided armoring
- Designed for accurate and repeatable measurements

Connector 1	Connector 2	Freq. Max (GHz)	Imp (Ohm)	VSWR	IL @fmax (dB/ft)	Phase Stability with Flexure (Degrees)	Flex Cycles	Model No	1	2-4	5-9	10+	ROW
2.4mm Male	2.4mm Male	50	50	1.300	3.7	6.00	100,000	PE3TC0500-24	$3,024.23	$2,903.26	$2,782.29	$2,661.32	63
					7			PE3TC0500-48	$3,179.00	$3,051.84	$2,924.68	$2,797.52	

Continued on Next Page

50 AND 67 GHZ TEST CABLE ASSEMBLIES

Product Features

- Highly flexible VNA test cables up to 50 and 67 GHz
- Max phase variation +/- 6˚ to 50 GHz and +/- 8˚ to 67 GHz with flexure
- VSWR of 1.3:1 to 50 GHz and 1.4:1 to 67 GHz
- Rated up to 5,000 mating cycles
- Up to 100,000 flex cycles
- Swept right angle connector options available
- Highly flexible stainless steel braided armoring
- Designed for accurate and repeatable measurements

Connector 1	Connector 2	Freq. Max (GHz)	Imp (Ohm)	VSWR	IL @fmax (dB/ft)	Phase Stability with Flexure (Degrees)	Flex Cycles	Model No	1	2-4	5-9	10+	ROW
2.4mm Male	2.4mm Female	50	50	1.300	3.7	6.00	100,000	PE3TC0600-24	$3,024.23	$2,903.26	$2,782.29	$2,661.32	64
					7			PE3TC0600-48	$3,179.00	$3,051.84	$2,924.68	$2,797.52	
	2.4mm Male Right Angle				3.7			PE3TC0700-24	$3,537.13	$3,395.64	$3,254.16	$3,112.67	65
					7			PE3TC0700-48	$3,688.49	$3,540.95	$3,393.41	$3,245.87	
1.85mm Male	1.85mm Male	67		1.400	4.3	8.00		PE3TC0800-24	$3,127.53	$3,002.43	$2,877.33	$2,752.23	66
					8.2			PE3TC0800-48	$3,279.23	$3,148.06	$3,016.89	$2,885.72	
	1.85mm Female				4.3			PE3TC0900-24	$3,127.53	$3,002.43	$2,877.33	$2,752.23	67
					8.2			PE3TC0900-48	$3,279.23	$3,148.06	$3,016.89	$2,885.72	
	1.85mm Male				4.3			PE3TC0800-500CM	Call	Call	Call	Call	68
	1.85mm Male Right Angle							PE3TC1000-24	$3,637.51	$3,492.01	$3,346.51	$3,201.01	69
					8.2			PE3TC1000-48	$3,792.44	$3,640.74	$3,489.04	$3,337.35	

1.0MM FLEXIBLE VNA 110 GHZ PRECISION CABLES

Product Features

- Operating to110 GHz
- Lightweight, protective armoring
- Precision 1.0mm stainless steel connectors
- Non-conductive protective Nome® outer sleever
- Easy assembly is serialized and includes test data

Connector 1	Connector 2	Freq. Max (GHz)	Imp (Ohm)	VSWR	IL @fmax (dB/ft)	Phase Stability with Flexure (Degrees)	Length (in)	Model No	1	2-4	5-9	10+	ROW
1.0mm Male	1.0mm Male	110	50	1.5	3.12	1.5	6.0	PE3TC1220-6	$6,373.75	$6,118.80	$5,863.85	$5,608.90	70
					5.62		12.0	PE3TC1220-12	$8,529.33	$8,188.16	$7,846.98	$7,505.81	
	1.0mm Female				3.12		6.0	PE3TC1221-6	$6,373.75	$6,150.67	$5,927.59	$5,736.38	71
					5.62		12.0	PE3TC1221-12	$6,652.90	$6,420.05	$6,187.20	$5,987.61	

PE-TC195 SERIES PHASE STABLE TEST CABLE ASSEMBLIES

Product Features

- Phase and amplitude stability with flexure
- Small diameter, lighter weight and lower profile for high density test applications
- Phase change with flexure +/-2° to 18 GHz
- Excellent for multi-port test equipment
- Very flexible and durable cable with a min. bend radius of 1 inch
- Excellent VSWR and insertion loss
- Extra strain relief for extended connector body with booting to enhance stability and longevity
- Each serialized assembly comes with matching test data
- 5,000 mating cycles when properly mated
- In-Stock and ready to ship

Connector 1	Connector 2	Freq. Max (GHz)	Imp (Ohm)	VSWR	IL (dB/ft)	IL (dB/m)	Phase Stability with Flexure (Degrees)	Flex Cycles	Model No	1 Pc. Price	See Web for Volume Pricing		ROW
N Male	N Female	18	50	1.25:1	0.68	2.23	2	75,000	PE3TC0104-24	$416.24		See Web for Volume Pricing	72
	N Male								PE3TC0103-24	$369.28			73
SMA Male									PE3TC0105-24	$357.55			74
	SMA Female								PE3TC0102-24	$386.89			75
		27			2.06	6.76	3		PE3TC0202-24	$600.12			76
	SMA Male	18			0.68	2.23	2		PE3TC0101-24	$339.94			77
		27			2.06	6.76	3		PE3TC0201-24	$492.52			78

See Web for other lengths

PE-TC151 SERIES PHASE STABLE TEST CABLE ASSEMBLIES

Product Features

- Phase and amplitude stability with flexure
- Small diameter, lighter weight and lower profile for high density test applications
- Phase change with flexure +/-5° to 18 GHz
- Excellent for multi-port test equipment
- Very flexible and durable cable with a min. bend radius of 0.75 inches
- Excellent VSWR and insertion loss
- Extra strain relief for extended connector body with booting to enhance stability and longevity
- Each serialized assembly comes with matching test data
- 5,000 mating cycles when properly mated
- In-Stock and ready to ship

Connector 1	Connector 2	Freq. Max (GHz)	Imp (Ohm)	VSWR	IL (dB/ft)	IL (dB/m)	Phase Stability with Flexure (Degrees)	Flex Cycles	Model No	1-9	10-24	25+	ROW
N Male	N Male	18	50	1.3:1	0.85	2.79	5	75,000	PE3TC0302-24	$301.67	$286.59	$271.50	79
SMA Male									PE3TC0303-24	$292.28	$277.67	$263.05	80
	SMA Male								PE3TC0301-24	$250.04	$237.54	$225.04	81
		27							PE3TC0401-24	$423.75	$402.56	$381.38	82

See Web for other lengths

75 OHM TEST CABLE ASSEMBLIES

Product Features

- Phase and amplitude stability with flexure
- Small diameter, lighter weight and lower profile for high density test applications
- Very flexible and durable cable with a min. bend radius of 0.75 inches
- Each serialized assembly comes with matching test data

Connector 1	Connector 2	Freq. Max (GHz)	Imp (Ohm)	VSWR	IL (dB/ft)	IL (dB/m)	Phase Stability with Flexure (Degrees)	Flex Cycles	Model No	1-9	10-24	25+	ROW
N Male	F Male	3	75	1.16:1	0.193	0.63	5	100,000	PE3CA1031-60cm	$284.41	$270.19	$255.97	83
	N Male								PE3CA1032-60cm	$323.03	$306.88	$290.73	84

See Web for other lengths

SEMI-RIGID PIGTAIL TEST PROBES

Product Features

- Operating to 6 GHz
- SMA Female connectors
- Excellent VSWR of 1.3:1
- Straight-cut and pre-stripped probe ends available



Connector 1	Cable	Lead	Freq. Max (GHz)	Imp (Ohm)	VSWR	IL @fmax (dB/ft)	Length (in)	Model No	1-24	25-49	50-99	100+	ROW
SMA Female	PE-020SR	Straight Cut Lead	6	50	1.35:1	0.43	3.0	PE3CA1107-3	$67.10	$63.75	$60.39	$57.71	85
		Trimmed Lead						PE3CA1104-3	$104.73	$99.49	$94.26	$90.07	86
	PE-034SR	Straight Cut Lead				0.28		PE3CA1102-3	$34.79	$33.05	$31.31	$29.92	87
		Trimmed Lead						PE3CA1105-3	$39.51	$37.53	$35.56	$33.98	88
	PE-047SR	Straight Cut Lead				0.20		PE3CA1103-3	$34.58	$32.85	$31.12	$29.74	89
		Trimmed Lead						PE3CA1106-3	$43.95	$41.75	$39.56	$37.80	90

See Web for other lengths

26.5 GHZ & 40 GHZ TEST CABLES

Product Features

- Rugged Armored Jacket
- 1.38 Inch [3.5cm] Bend Radius
- RoHS Compliant

Connector 1	Connector 2	Freq. Max (GHz)	Imp (Ohm)	VSWR	IL @fmax (dB/ft)	Length (in)	Model No	1	2-4	5-9	10+	ROW
3.5mm Male	3.5mm Male	26.5	50	1.25	0.64	Various	PE3VNA2603	Call	Call	Call	Call	91
3.5mm Female	3.5mm Female			1.3			PE3VNA2604					92
2.92mm Male	2.92mm Male			1.25			PE3VNA2605					93
							PE3VNA2606					94
		40		1.38	0.83		PE3VNA4001					95
2.92mm Female	2.92mm Female						PE3VNA4002					96
2.4mm Male	2.4mm Male						PE3VNA4004					97
2.4mm Female	2.4mm Female						PE3VNA4005					98

INDEX GUIDE TO
TOOLS

TOOLS.....355

CABLE CUTTER.....355

CRIMP TOOL DIES.....357

CRIMP TOOLS.....357

INSERTION / EXTRACTION TOOL.....355

TORQUE WRENCHES.....356

TOOLS

Cable Cutter

Type	Coax/Wire Type	Model No	1-24	25-49	50-99	100+	ROW
Cable Cutter	Coax	PE5200	$104.64	$99.41	$94.18	$89.99	1

Insertion/Extraction Tool

Type	Connector Type	Model No	1-24	25-49	50-99	100+	ROW
Insertion/Extraction Tool	BNC	PE5014	Call	Call	Call	Call	2

Torque Wrenches

Type	Bit Hex Size	Preset Torque (in.-lbs)	Design	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
1.0mm	15/64 inch	4	Break-Over	PE5019-16	$242.40		See Web for Volume Pricing		
3.5mm, 2.92mm	5/16 inch	8		PE5019-1	$210.86				3
		12		PE5019-2	$227.60				
7mm	3/4 inch	14	Click Type	PE5011-3	$394.41				4
N	20 mm	8.1	Break-Over	PE5019-5	$242.40				3
		14	Click Type	PE5011-7	$318.02				4
	25/32 inch		Break-Over	PE5019-6	$240.14				
	3/4 inch	8.1		PE5019-3	$240.14				
N, 7mm		14		PE5019-4	$240.14				3
N, SC	13/16 inch	8.1		PE5019-7	$240.14				
		14	Click Type	PE5011-6	$383.61				4
			Break-Over	PE5019-8	$240.14				
SMA	5/16 inch	5		PE5019-19	$223.35				3
SMA, 2.92mm		8	Click Type	PE5011-1	$256.76				
SMC	1/4 inch	3		PE5011-2	$354.79				4
	15/64 inch		Break-Over	PE5019-11	$242.40				
SSMA	1/4 inch	5		PE5019-13	$242.40				3
		8	Click Type	PE5011-5	$363.11				4
		8.1	Break-Over	PE5019-14	$242.40				
SSMC	5/32 inch	2		PE5019-12	$240.14				
TNC	5/8 inch	6.1		PE5019-18	$259.38				3
		12		PE5019-10	$240.14				
		14	Click Type	PE5011-4	$360.10				4
	9/16 inch	6.1	Break-Over	PE5019-17	$242.40				
		12		PE5019-9	$240.14				3
		13	Click Type	PE5011-8	$339.73				4

Crimp Tools

Type	Hex Size (in.)	Compatible Dies	Cable Type	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
Crimp Tools	0.068, 0.100, 0.128, 0.178	- - -	RG174,RG179, RG180, RG187, RG188, RG195, RG316	PE5006	$167.48		See Web for Volume Pricing		5
	0.068, 0.213, 0.255		RG55, RG58, RG59, RG62, RG142, RG223 RG400	PE5001	$149.61				6
	0.100, 0.429		RG9, RG11, RG87A, RG149, RG165, RG213, RG214, RG216, RG225, RG393	PE5007	$177.15				7
Crimp Tool Kit	0.042, 0.068, 0.080, 0.100, 0.128, 0.151, 0.178, 0.213, 0.255, 0.324, 0.429	- - -	RG5, RG6, RG8, RG9, RG11, RG21, RG55, RG58, RG59, RG62, RG87A, RG140, RG141, RG142, RG143, RG165, RG174, RG179, RG180, RG187, RG188, RG195, RG210, RG212, RG213, RG214, RG216, RG222, RG223, RG225, RG303, RG304, RG316, RG393, RG400	PE5004-KIT	$403.61				8
Crimp Tool, Scissor style, No Die	- - -	PE5010-1, PE5010-2, PE5010-3, PE5010-4, PE5010-5 and PE5010-6	- - -	PE5008	$458.07				9
Crimp Tool, Straight Style, No Die	- - -	PE5010-1, PE5010-2, PE5010-3, PE5010-4, PE5010-5 and PE5010-6	- - -	PE5009	$232.97				10
Crimp Tool for Compression Connectors	- - -	- - -	RG6, RG11, RG59	PE5012	$158.60				11

Crimp Tool Dies

Type	Hex Size (in.)	Compatible Crimp Tools	Cable Type	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
Dies, Crimp Tool	0.128, 0.100	PE5008 and PE5009	RG174, RG178, RG179, RG188, RG196, RG316	PE5010-2	$225.30		See Web for Volume Pricing		12
	0.213, 0.068		RG58, RG142, RG223, RG400	PE5010-1	$298.05				
	0.255, 0.068		RG8X, RG59, RG62, PE-C240	PE5010-3	$266.11				
	0.429, 0.100		RG8, RG213, RG214, PE-B400, PE-B405, PE-C400	PE5010-5	$234.09				

INDEX GUIDE TO
WAVEGUIDE PRODUCTS

WAVEGUIDE ANTENNAS....360

WAVEGUIDE ANTENNAS....360 | *WG ANTENNA ACCESSORIES....365*

Pasternack offers a large selection of waveguide antennas from WR-284 to WR-15 (2.6 GHz to 75 GHz) in a variety of flanges and gain. Both UG and CPR/CMR style flanges are available. Most of the gain horn antennas can be purchased already assembled with a waveguide to coax adapter.

WAVEGUIDE BENDS....369

Pasternack offers a selection of E and H plane waveguide bends of various flanges and interfaces, covering the frequency range from 5.85 GHz to 18 GHz with VSWR as low as 1.08:1.

WAVEGUIDE FILTERS....369

BANDPASS....369

Pasternack offers a selection of high performance waveguide bandpass filters, covering the frequency range from 20.2 GHz to 40 GHz with WR-28 and WR-42 interfaces. These filters exhibit excellent out-of-band rejection making them ideally suited to receiver front-end or transmitter applications.

WAVEGUIDE BULKHEAD ADAPTERS....370

The Pasternack series of rectangular waveguide bulkhead flange mount adapters are mounted to the panel of equipment with screws. Once mounted, waveguides flanges can be attached to the adapter on both sides of the bulkhead adapter to allow a signal path through the panel.

WAVEGUIDE CONVERTERS....371

MIXER DOWN CONVERTERS....371 | *MIXER UP CONVERTERS....371*

Pasternack offers a series of Millimeter Wave Up and Down Converter Mixers that cover popular Ka, Q, U, V, E, and W Bands up to 110 GHz with an IF frequency of DC to 18 GHz. L and R ports support popular waveguide sizes from WR-28 to WR-10, and the IF port utilize Female SMA connectors.

WAVEGUIDE COUPLERS....371

ASSEMBLIES....376 | *BROADWALL....371* | *CROSSGUIDE....372*

Pasternack offers a brand new family of instrumentation grade directional waveguide couplers boasting accurate performance up to 110 GHz in seven popular frequency bands including K, Ka, Q, U, V, E and W bands. These waveguide couplers boast high directivity of 30 dB typical and insertion loss is as low as 0.6 dB in some models.

WAVEGUIDE DETECTORS....377

Waveguide detectors consists of 6 unique models covering a broad frequency range of 26.5 GHz to 110 GHz. The input ports use popular waveguide sizes ranging from WR-28 to WR-10, while the video output ports utilize SMA female connectors. The detector circuits use high performance GaAs Schottky Barrier Beam lead diodes with extremely low junction capacitance.

WAVEGUIDE DIRECT READ ATTENUATORS....377

These continuously variable attenuators have “direct read” capability which allows the user to dial-in the amount of attenuation needed to within 2% accuracy over most of the attenuation range. The attenuation level is stable, highly repeatable and accurate across the full frequency and attenuation range. These attenuators are ideal for precision measurements in demanding applications like instrumentation and system calibration.

WAVEGUIDE ELECTROMECHANICAL RELAY SWITCHES....377

Pasternack offers a series of 28 waveguide electromechanical relay switch models that offer full waveguide performance covering C, X, Ku, K and Ka frequency bands from 5.85 GHz 40 GHz. These switches re configured for single-pole double-throw (SPDT) operation with latching self-cut-off actuators, TTL logic and position indicators with manual override.

WAVEGUIDE FIXED ATTENUATORS....379

Pasternack's wide selection of waveguide fixed attenuator products offers precision attenuation levels over the operating frequency ranges.

FLEXIBLE WAVEGUIDES....380

SEAMLESS....380 *TWISTABLE....380*

This family of flexible, seamless waveguides or flexible, twistable waveguides that can be bent in both the E and H planes without impairing VSWR or attenuation. These waveguides are covered by a neoprene jacket which protect the waveguide and provides mechanical support.

WAVEGUIDE GUNN OSCILLATORS....381

Waveguide Gunn Oscillators consist of 2 models that have center frequencies of 24.125 GHz and 35 GHz. Both models are tunable and supply output power levels of +10 dBm min. Compact package outlines support WR-28 and WR-42 waveguide sizes.



WAVEGUIDE ISOLATORS.... 381

Pasternack Enterprises offers a wide variety of waveguide isolators from WR-10 to WR-112.

WAVEGUIDE POWER AMPLIFIERS....383

Waveguide Power Amplifiers consist of 2 models that cover 70.5 GHz to 86.5 GHz (E Band) and support WR-12 waveguide ports.

WG LOW NOISE AMPLIFIERS....382

Pasternack WG Low Noise Amplifiers are ruggedly built 50 ohm designs and unconditionally stable with impressive performance across freq. bands.

WAVEGUIDE SECTIONS.... 383

Pasternack offers a standard product line of waveguide straight section of various length and flanges, covering the frequency range from 5.85 GHz to 12.4 GHz.

WAVEGUIDE MAGIC TEES.... 382

Pasternack's magic, or hybrid tees are 4 port device that is internally tuned to optimize matching, balance, and isolation.

WAVEGUIDE TERMINATIONS....385

Pasternack has a large family of high performance loads from WR-112 to WR-10. These standard terminations can dissipate up to 300 Watts of power depending on the specific band.

WG ORTHOMODE TRANSDUCERS....382

These Orthomode Transducers are used for separating signals into two linear orthogonal signals. Pasternack's OMT line support from 8.2 to 90 GHz with 30-35 dB of isolation between ports.

WAVEGUIDE TRANSITIONS....386

Pasternack's family of Waveguide Transitions/Adapters are used as a means of propagating RF/ Microwave energy from one waveguide size to another.

WAVEGUIDE PHASE SHIFTERS....382

These waveguide variable phase shifters are built using low loss dielectric material, which offers minimum insertion loss..

WAVEGUIDE TWISTS....387

Pasternack offers waveguide twists in 45 degree left and right hand waveguide versions as well at 90 degree. These twists are designed and constructed to prevent unwanted distortion to the signal's transmission.

WAVEGUIDE PIN DIODE SWITCHES....383

Waveguide PIN Diode Switches consist of 4 models that cover 60 GHz to 110 GHz, in both SPST and SPDT configurations.

WAVEGUIDE VARIABLE ATTEN.... 388

The Continuously Variable attenuators are equipped with a micrometer, which enables rapid re-setting. With calibrated charts, attenuators can be used as direct reading attenuator for bench top test set use.

WAVEGUIDE POLARIZERS....383

Pasternack's Waveguide Polarizers transform polarized signals from circular to linear and vice versa. They can operate as either right hand or left hand polarization. Waveguide Polarizers currently cover Ku, Ka, and V bands.

WAVEGUIDE ACCESSORIES....388



Pasternack Enterprises offers a variety of waveguide accessories from WR-10 to WR-430.

WAVEGUIDE ANTENNAS

Waveguide Antennas With Coax Adapters




Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-28	26.5 - 40	10	WR-28 - 2.92mm Female	EAR99	PE9850B/2F-10	$1,804.73	$1,732.54	$1,660.35	$1,588.16	1
		15		EAR99	PE9850B/2F-15	$1,874.15	$1,799.18	$1,724.22	$1,649.25	2
		20		EAR99	PE9850B/2F-20	$1,993.16	$1,913.43	$1,833.71	$1,753.98	3
WR-34	22 - 33	10	WR-34 - 2.92mm Female	EAR99	PE9851B/2F-10	$1,859.96	$1,785.56	$1,711.16	$1,636.76	4
		15		EAR99	PE9851B/2F-15	$2,003.80	$1,923.65	$1,843.50	$1,763.34	5
		20		EAR99	PE9851B/2F-20	$2,140.33	$2,054.72	$1,969.10	$1,883.49	6
WR-42	18 - 26.5	10	WR-42 - 2.92mm Female	EAR99	PE9852B/2F-10	$1,617.15	$1,552.46	$1,487.78	$1,423.09	7
		15		EAR99	PE9852B/2F-15	$1,713.90	$1,645.34	$1,576.79	$1,508.23	8
		20		EAR99	PE9852B/2F-20	$1,840.31	$1,766.70	$1,693.09	$1,619.47	9
WR-51	15 - 22	10	WR-51 - SMA Female	EAR99	PE9853B/SF-10	$1,638.30	$1,572.77	$1,507.24	$1,441.70	10
		15		EAR99	PE9853B/SF-15	$1,757.92	$1,687.60	$1,617.29	$1,546.97	11
WR-62	12.4 - 18	10	WR-62 - N Female	EAR99	PE9854B/NF-10	$1,411.63	$1,355.16	$1,298.70	$1,242.23	12
		15		EAR99	PE9854B/NF-15	$1,457.70	$1,399.39	$1,341.08	$1,282.78	13
		20		EAR99	PE9854B/NF-20	$1,552.92	$1,490.80	$1,428.69	$1,366.57	14
		10	WR-62 - SMA Female	EAR99	PE9854B/SF-10	$1,411.28	$1,354.83	$1,298.38	$1,241.93	15
		15		EAR99	PE9854B/SF-15	$1,457.26	$1,398.97	$1,340.68	$1,282.39	16
		20		EAR99	PE9854B/SF-20	$1,549.69	$1,487.70	$1,425.71	$1,363.73	17
WR-75	10 - 15	10	WR-75 - N Female	EAR99	PE9855B/NF-10	$1,432.55	$1,375.25	$1,317.95	$1,260.64	19
		15		EAR99	PE9855B/NF-15	$1,454.53	$1,396.35	$1,338.17	$1,279.99	18
		20		EAR99	PE9855B/NF-20	$1,515.55	$1,454.93	$1,394.31	$1,333.68	19
		10	WR-75 - SMA Female	EAR99	PE9855B/SF-10	$1,404.00	$1,347.84	$1,291.68	$1,235.52	21
		15		EAR99	PE9855B/SF-15	$1,448.05	$1,390.13	$1,332.21	$1,274.28	20
		20		EAR99	PE9855B/SF-20	$1,509.07	$1,448.71	$1,388.34	$1,327.98	21
WR-90	8.2 - 12.4	10	WR-90 - N Female	EAR99	PE9856B/NF-10	$1,342.40	$1,288.70	$1,235.01	$1,181.31	22
		15		EAR99	PE9856B/NF-15	$1,434.43	$1,377.05	$1,319.68	$1,262.30	23
		20		EAR99	PE9856B/NF-20	$1,496.71	$1,436.84	$1,376.97	$1,317.10	24
		10	WR-90 - SMA Female	EAR99	PE9856B/SF-10	$1,288.52	$1,236.98	$1,185.44	$1,133.90	25
		15		EAR99	PE9856B/SF-15	$1,434.43	$1,377.05	$1,319.68	$1,262.30	26
		20		EAR99	PE9856B/SF-20	$1,506.26	$1,446.01	$1,385.76	$1,325.51	27
WR-102	7 - 11	10	WR-102 - N Female	EAR99	PE9857B/NF-10	$1,499.63	$1,439.64	$1,379.66	$1,319.67	28
		15		EAR99	PE9857B/NF-15	$1,604.76	$1,540.57	$1,476.38	$1,412.19	
		20		EAR99	PE9857B/NF-20	$1,650.13	$1,584.12	$1,518.12	$1,452.11	29
		10	WR-102 - SMA Female	EAR99	PE9857B/SF-10	$1,556.07	$1,493.83	$1,431.58	$1,369.34	30
		10		EAR99	PE9857B/SF-15	$1,628.08	$1,562.96	$1,497.83	$1,432.71	
		20		EAR99	PE9857B/SF-20	$1,706.57	$1,638.31	$1,570.04	$1,501.78	31
WR-112	7.05 - 10	10	WR-112 - N Female	EAR99	PE9858B/NF-10	$1,466.30	$1,407.65	$1,349.00	$1,290.34	32
		15		EAR99	PE9858B/NF-15	$1,536.94	$1,475.46	$1,413.98	$1,352.51	
		20		EAR99	PE9858B/NF-20	$1,653.66	$1,587.51	$1,521.37	$1,455.22	33
		10	WR-112 - SMA Female	EAR99	PE9858B/SF-10	$1,425.14	$1,368.13	$1,311.13	$1,254.12	34
		15		EAR99	PE9858B/SF-15	$1,520.62	$1,459.80	$1,398.97	$1,338.15	
		20		EAR99	PE9858B/SF-20	$1,612.50	$1,548.00	$1,483.50	$1,419.00	35
WR-137	5.85 - 8.2	10	WR-137 - N Female	EAR99	PE9859B/NF-10	$1,575.07	$1,512.07	$1,449.06	$1,386.06	36
		15		EAR99	PE9859B/NF-15	$1,636.97	$1,571.49	$1,506.01	$1,440.53	37
		10	WR-137 - SMA Female	EAR99	PE9859B/SF-10	$1,575.07	$1,512.07	$1,449.06	$1,386.06	38
		15		EAR99	PE9859B/SF-15	$1,636.97	$1,571.49	$1,506.01	$1,440.53	39
WR-159	4.9 - 7.05	15	WR-159 - N Female	EAR99	PE9860B/NF-15	$1,891.63	$1,815.96	$1,740.30	$1,664.63	40
		15	WR-159 - SMA Female	EAR99	PE9860B/SF-15	$1,884.43	$1,809.05	$1,733.68	$1,658.30	41
WR-284	2.6 - 3.95	10	WR-284 - N Female	EAR99	PE9863B/NF-10	$2,542.84	$2,441.13	$2,339.41	$2,237.70	42
		10	WR-284 - SMA Female	EAR99	PE9863B/SF-10	$2,865.50	$2,750.88	$2,636.26	$2,521.64	43
WR-430	1.7 - 2.6	10	WR-430 - N Female	EAR99	PE9864B/NF-10	$3,107.39	$2,983.09	$2,858.80	$2,734.50	44
		15		EAR99	PE9864B/NF-15	$3,933.64	$3,776.29	$3,618.95	$3,461.60	
		10	WR-430 - SMA Female	EAR99	PE9864B/SF-10	$3,078.69	$2,955.54	$2,832.39	$2,709.25	45
		15		EAR99	PE9864B/SF-15	$4,063.50	$3,900.96	$3,738.42	$3,575.88	

Standard Gain Horns

Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
WR-5	140 - 220	10	Round Cover UG-387/U-Mod	EAR99	PEWAN1029	$2,217.19		See Web for Volume Pricing		46
		15		EAR99	PEWAN1030	$2,217.19				47
		20		EAR99	PEWAN1031	$2,217.19				48
		25		EAR99	PEWAN1032	$2,325.40				49
WR-6	110 - 170	10		EAR99	PEWAN1025	$1,814.07				50
		15		EAR99	PEWAN1026	$1,840.94				51
		20		EAR99	PEWAN1027	$1,867.82				52
		25		EAR99	PEWAN1028	$2,196.44				53
WR-8	90 - 140	10		EAR99	PEWAN1021	$1,545.32				54
		15		EAR99	PEWAN1022	$1,572.19				55
		20		EAR99	PEWAN1023	$1,599.07				56
		25		EAR99	PEWAN1024	$2,015.63				57
WR-10	75 - 110	10		EAR99	PEWAN1017	$1,295.68				58
		15		EAR99	PEWAN1018	$1,303.44				59
		20		EAR99	PEWAN1019	$1,402.89				60
		25		EAR99	PEWAN1020	$1,773.03				61
WR-12	60 - 90	10		EAR99	PEWAN1013	$1,346.21				62
		15		EAR99	PEWAN1014	$1,374.55				63
		20		EAR99	PEWAN1015	$1,402.89				64
		25	Round Cover UG-387/U	EAR99	PEWAN1016	$1,842.19				65
WR-15	50 - 75	10	Round Cover UG-385/U-Mod	EAR99	PEWAN1009	$1,295.68				66
		15		EAR99	PEWAN1010	$1,374.55				67
		20		EAR99	PEWAN1011	$1,330.32				68
		24	Round Cover UG-385/U	EAR99	PE9881-24	$1,613.93				69
		25	Round Cover UG-385/U-Mod	EAR99	PEWAN1012	$1,842.19				70
WR-19	40 - 60	10	Round Cover UG-383/U-Mod	EAR99	PEWAN1005	$1,417.07				71
		15		EAR99	PEWAN1006	$1,472.98				72
		20		EAR99	PEWAN1007	$1,500.26				73
		25		EAR99	PEWAN1008	$1,773.03				74
WR-28	26.5 - 40	10	Square Cover UG-599/U	EAR99	PE9850B-10	$931.16				75
		15		EAR99	PE9850B-15	$1,116.93				76
		20		EAR99	PE9850B-20	$1,054.14				77
WR-34	22 - 33	10	Square Cover UG-1530/U	EAR99	PE9851B-10	$903.79				78
		15		EAR99	PE9851B-15	$1,039.53				79
		20		EAR99	PE9851B-20	$1,176.05				80
WR-42	18 - 26.5	10	Square Cover UG-597/U	EAR99	PE9852B-10	$903.24				81
		15		EAR99	PE9852B-15	$1,046.79				82
		20		EAR99	PE9852B-20	$1,178.54				83
WR-51	15 - 22	10	Square Cover	EAR99	PE9853B-10	$812.95				84
		15		EAR99	PE9853B-15	$876.00				85
		20		EAR99	PE9853B-20	$920.32				86
WR-62	12.4 - 18	10	Square Cover UG-1665/U	EAR99	PE9854B-10	$924.50				87
		15	Square Cover	EAR99	PE9854B-15	$967.50				88
		20		EAR99	PE9854B-20	$1,134.84				89
WR-75	10 - 15	10		EAR99	PE9855B-10	$954.95				90
		15		EAR99	PE9855B-15	$1,012.25				91
		20		EAR99	PE9855B-20	$1,021.25				92
WR-90	8.2 - 12.4	10	Square Cover UG-135/U	EAR99	PE9856B-10	$916.39				93
		15		EAR99	PE9856B-15	$1,065.35				94
		20		EAR99	PE9856B-20	$1,116.61				95
WR-102	7 - 11	10	Square Cover UG-1493/U	EAR99	PE9857B-10	$903.79				96
		15	Square Cover	EAR99	PE9857B-15	$908.42				97
		20	Square Cover UG-1493/U	EAR99	PE9857B-20	$963.20				98
WR-112	7.05 - 10	10	Square Cover	EAR99	PE9858B-10	$994.16				99
		15	Square Cover UG-138/U	EAR99	PE9858B-15	$1,069.21				1
		20	Square Cover	EAR99	PE9858B-20	$1,144.88				2
WR-137	58.5 - 82	20	CMR-137F	EAR99	PE9859B-20	$1,075.00				3
	5.85 - 8.2	10	CMR-137	EAR99	PE9859B-10	$929.13				4
		15		EAR99	PE9859B-15	$989.77				5
WR-159	49 - 70.5	20	CMR-159	EAR99	PE9860B-20	Call				6

See Our Website For Current Pricing & Real-Time Stock Availability!

Standard Gain Horns



Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1-4	5-9	10-24	25+	ROW
WR-159	4.9 - 7.05	10	CMR-159	EAR99	PE9860B-10	$983.32	$934.15	$884.99	$845.66	7
		15		EAR99	PE9860B-15	$1,057.20	$1,004.34	$951.48	$909.19	8
WR-187	3.95 - 5.85	10	CMR-187	EAR99	PE9861B-10	$1,075.00	$1,021.25	$967.50	$924.50	9
WR-229	33 - 49	20	CMR-229	EAR99	PE9862B-20	$1,705.40	$1,620.13	$1,534.86	$1,466.64	10
	3.3 - 4.9	15		EAR99	PE9862B-15	$1,359.99	$1,291.99	$1,223.99	$1,169.59	11
WR-284	26 - 39.5	15	CMR-284	EAR99	PE9863B-15	$1,827.50	$1,736.13	$1,644.75	$1,571.65	12
		15	Round Cover UG-584/U	EAR99	PE9863B-15-U	$1,720.00	$1,634.00	$1,548.00	$1,479.20	13
		20		EAR99	PE9863B-20-U	$1,914.19	$1,818.48	$1,722.77	$1,646.20	14
	2.6 - 3.95	10	CMR-284	EAR99	PE9863B-10	$1,393.82	$1,324.13	$1,254.44	$1,198.69	15
		10	Round Cover UG-584/U		PE9863B-10-U	$1,526.50	$1,450.18	$1,373.85	$1,312.79	16
WR-430	17 - 26	10	CPR-430F	EAR99	PE9864B-10	$1,827.77	$1,736.38	$1,644.99	$1,571.88	17

Conical Gain Horns

Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-5	140 - 220	10	Round Cover UG-387/U	EAR99	PEWAN1065	$2,163.44	See Web for Volume Pricing	18
		15		EAR99	PEWAN1066	$2,190.32		19
		20		EAR99	PEWAN1067	$2,217.19		20
		25		EAR99	PEWAN1068	$2,416.09		21
WR-6	100 - 112	10	Round Cover UG-387/U-Mod	EAR99	PEWAN1061	$1,814.07		22
		15		EAR99	PEWAN1062	$1,840.94		23
		20		EAR99	PEWAN1063	$1,867.82		24
		25		EAR99	PEWAN1064	$2,082.82		25
WR-8		10		EAR99	PEWAN1057	$1,303.44		26
		15		EAR99	PEWAN1058	$1,330.32		27
		20		EAR99	PEWAN1059	$1,478.13		28
		25		EAR99	PEWAN1060	$1,746.88		29
WR-10	87 - 100	10	Round Cover UG-387/U	EAR99	PEWAN1049	$1,303.44		30
		15		EAR99	PEWAN1050	$1,330.32		31
		20		EAR99	PEWAN1051	$1,478.13		32
		25		EAR99	PEWAN1052	$1,773.03		33
	77 - 87	10		EAR99	PEWAN1053	$1,303.44		34
		15		EAR99	PEWAN1054	$1,330.32		35
		20		EAR99	PEWAN1055	$1,478.13		36
		25		EAR99	PEWAN1056	$1,746.88		37
WR-12		10		EAR99	PEWAN1045	$1,303.44		38
		15		EAR99	PEWAN1046	$1,330.32		39
		20		EAR99	PEWAN1047	$1,478.13		40
		25		EAR99	PEWAN1048	$1,746.88		41
	68 - 77	10		EAR99	PEWAN1041	$1,303.44		42
		15		EAR99	PEWAN1042	$1,330.32		43
		20		EAR99	PEWAN1043	$1,478.13		44
		25		EAR99	PEWAN1044	$1,746.88		45
WR-15	58 - 68	10	Round Cover UG-385/U	EAR99	PEWAN1037	$1,303.44		46
		15		EAR99	PEWAN1038	$1,350.24		47
		20		EAR99	PEWAN1039	$1,478.13		48
		25		EAR99	PEWAN1040	$1,746.88		49
WR-19	50 - 58	10	Round Cover UG-383/U-Mod	EAR99	PEWAN1033	$1,182.50		50
		15		EAR99	PEWAN1034	$1,330.32		51
		20		EAR99	PEWAN1035	$1,478.13		52
		25		EAR99	PEWAN1036	$1,773.03		53

Wide Angle Scalar Feed Horns

Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-10	89 - 99	10	Round Cover UG-385/U-Mod	EAR99	PEWAN1073	$5,079.38	$4,901.60	$4,723.82	$4,571.44	54
		10		EAR99	PEWAN1074	$3,574.38	$3,449.28	$3,324.17	$3,216.94	55
WR-12	72 - 82	10	Round Cover UG-385/U	EAR99	PEWAN1071	$5,155.41	$4,974.97	$4,794.53	$4,639.87	56
		10		EAR99	PEWAN1072	$3,574.38	$3,449.28	$3,324.17	$3,216.94	57
WR-15	55 - 65	10		EAR99	PEWAN1069	$5,079.38	$4,901.60	$4,723.82	$4,571.44	58
		10		EAR99	PEWAN1070	$3,769.38	$3,637.45	$3,505.52	$3,392.44	59

Lens Gain Horns

Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-10	89 - 99	34	Round Cover UG-387/U	EAR99	PEWAN1083	$5,079.38	See Web for Volume Pricing	60
		34		EAR99	PEWAN1085	$6,208.13		61
		40		EAR99	PEWAN1084	$5,537.30		62
		40		EAR99	PEWAN1086	$6,584.38		63
	88 - 100	40	Round Cover UG-387/U-Mod	EAR99	PEWAN1101	$10,054.62		64
		48	Square Cover UG-387/U-Mod	EAR99	PEWAN1102	$10,330.09		65
WR-12	72 - 82	32	Round Cover UG-387/U	EAR99	PEWAN1079	$4,326.88		66
		32		EAR99	PEWAN1081	$5,455.63		67
		37		EAR99	PEWAN1080	$4,703.13		68
		37		EAR99	PEWAN1082	$5,831.88		69
WR-15	55 - 65	32	Round Cover UG-385/U	EAR99	PEWAN1075	$3,198.13		70
		32		EAR99	PEWAN1077	$4,326.88		71
		37		EAR99	PEWAN1076	$3,574.38		72
		37		EAR99	PEWAN1078	$4,703.13		73

Omni-Directional

Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-10	90 - 100	0	Round Cover UG-387/U-Mod	EAR99	PEWAN1135	$4,971.88	$4,797.86	$4,623.85	$4,474.69	74
		6.5	Square Cover UG-387/U-Mod	EAR99	PEWAN1136	$4,971.88	$4,797.86	$4,623.85	$4,474.69	75
	89 - 99	2	Round Cover UG-387/U	EAR99	PEWAN1089	$7,446.71	$7,186.08	$6,925.44	$6,702.04	76
WR-12	75 - 79	2		EAR99	PEWAN1088	$7,336.88	$7,080.09	$6,823.30	$6,603.19	77
	71 - 86	2		EAR99	PEWAN1134	$4,703.13	$4,538.52	$4,373.91	$4,232.82	78
WR-15	58 - 62	3.5	Round Cover UG-385/U	EAR99	PEWAN1087	$7,446.71	$7,186.08	$6,925.44	$6,702.04	79
WR-28	26.5 - 40	7.5	Square Cover UG-599/U	EAR99	PEWAN1133	$4,165.63	$4,019.83	$3,874.04	$3,749.07	80

Probe Waveguide Antennas

Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-6	110 - 170	6.5	Round Cover UG-387/U-Mod	EAR99	PEWAN1124	$1,882.15	$1,816.27	$1,750.40	$1,693.94	81
WR-8	90 - 140	6.5		EAR99	PEWAN1125	$1,854.38	$1,789.48	$1,724.57	$1,668.94	82
WR-10	75 - 110	6.5		EAR99	PEWAN1126	$1,854.38	$1,789.48	$1,724.57	$1,668.94	83

Probe Waveguide Antennas

Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-12	60 - 90	6.5	Round Cover UG-387/U	EAR99	PEWAN1127	$1,882.15	$1,816.27	$1,750.40	$1,693.94	84
WR-15	50 - 75	6.5	Round Cover UG-385/U	EAR99	PEWAN1128	$1,854.38	$1,789.48	$1,724.57	$1,668.94	85
WR-19	40 - 60	6.5	Round Cover UG-383/U-Mod	EAR99	PEWAN1129	$1,854.38	$1,789.48	$1,724.57	$1,668.94	86
WR-22	33 - 50	6.5	Round Cover UG-383/U	EAR99	PEWAN1130	$1,854.38	$1,789.48	$1,724.57	$1,668.94	87
WR-28	26.5 - 40	6.5	Square Cover UG-599/U	EAR99	PEWAN1131	$1,882.15	$1,816.27	$1,750.40	$1,693.94	88
WR-34	22 - 33	6.5	Square Cover UG-1530/U	EAR99	PEWAN1132	$1,882.15	$1,816.27	$1,750.40	$1,693.94	89

Sector Waveguide Antennas

Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-28	30 - 40	0	Square Cover UG-599/U-Mod	EAR99	PEWAN1144	$3,440.00	$3,319.60	$3,199.20	$3,096.00	90
	27.5 - 29.5	6	Square Cover UG-599/U	EAR99	PEWAN1143	$3,491.51	$3,369.31	$3,247.10	$3,142.36	91

Dual Polarized Scalar Feed Horns

Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
	100 - 112	17	Round Cover UG-387/U-Mod	EAR99	PEWAN1109	$5,509.38	$5,316.55	$5,123.72	$4,958.44	92
	87 - 100	17	UG-387/U-Mod	EAR99	PEWAN1123	$4,971.88	$4,797.86	$4,623.85	$4,474.69	93
	77 - 87	17		EAR99	PEWAN1122	$4,837.50	$4,668.19	$4,498.88	$4,353.75	94
WR-10	75 - 110	13		EAR99	PEWAN1121	$20,290.63	$19,580.46	$18,870.29	$18,261.57	95
		15	Square Cover UG-387/U-Mod	EAR99	PEWAN1137	$9,271.88	$8,947.36	$8,622.85	$8,344.69	96
		20		EAR99	PEWAN1141	$9,271.88	$8,947.36	$8,622.85	$8,344.69	97
	68 - 77	17	UG-387/U-Mod	EAR99	PEWAN1120	$4,837.50	$4,668.19	$4,498.88	$4,353.75	98
WR-12	60 - 90	13	UG-387/U	EAR99	PEWAN1119	$19,753.13	$19,061.77	$18,370.41	$17,777.82	99
		15	Square Cover UG-387/U	EAR99	PEWAN1138	$8,734.38	$8,428.68	$8,122.97	$7,860.94	1
	58 - 68	17	UG-385/U-Mod	EAR99	PEWAN1118	$4,703.13	$4,538.52	$4,373.91	$4,232.82	2
WR-12	50 - 75	15	Square Cover UG-385/U	EAR99	PEWAN1139	$8,062.50	$7,780.31	$7,498.13	$7,256.25	3
WR-15		13	UG-385/U-Mod	EAR99	PEWAN1117	$20,290.63	$19,580.46	$18,870.29	$18,261.57	4
WR-19	40 - 60	13	UG-383/U-Mod	EAR99	PEWAN1116	$16,528.13	$15,949.65	$15,371.16	$14,875.32	5
WR-22	33 - 50	15	Square Cover UG-383/U	EAR99	PEWAN1140	$7,525.00	$7,261.63	$6,998.25	$6,772.50	6
	33 - 38.5	17	UG-599/U	EAR99	PEWAN1115	$4,300.00	$4,149.50	$3,999.00	$3,870.00	7
	26 - 33	17		EAR99	PEWAN1114	$4,300.00	$4,149.50	$3,999.00	$3,870.00	8
WR-28	26 - 30	17		EAR99	PEWAN1113	$4,300.00	$4,149.50	$3,999.00	$3,870.00	9
	24 - 42	10	Square Choke UG-599/U	EAR99	PEWAN1142	$10,750.00	$10,373.75	$9,997.50	$9,675.00	10
	24 - 40	15	UG-599/U	EAR99	PEWAN1111	$12,547.57	$12,108.41	$11,669.24	$11,292.81	11
	24 - 42	15		EAR99	PEWAN1112	$13,706.25	$13,226.53	$12,746.81	$12,335.63	12
	24 - 33	16	Square Cover UG-1530/U	EAR99	PEWAN1110	$4,300.00	$4,149.50	$3,999.00	$3,870.00	13

Specialty Waveguide Antennas

Waveguide Type	RF Frequency (GHz.)	Gain (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
Broadband	1 - 18			EAR99	PE9887-11	$3,872.33	$3,736.80	$3,601.27	$3,485.10	14
				EAR99	PE9888-11	$3,565.14	$3,440.36	$3,315.58	$3,208.63	15
WR-15	50 - 75	42	Round Cover - UG-385/U	5A991	PE9881-42	$2,798.32	$2,686.39	$2,574.45	$2,462.52	16
		20		EAR99	PE9881A-20	$1,182.42	$1,135.12	$1,087.83	$1,040.53	17
				EAR99	PEW15A001	$4,274.59	$4,124.98	$3,975.37	$3,847.13	18
	56.5 - 67			5A991	PE9881-34	$1,694.40	$1,635.10	$1,575.79	$1,524.96	19

WAVEGUIDE ANTENNA ACCESSORIES

Waveguide to Coax Adapters

WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Flange Type	Connector	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-10	75-110	1	1.32:1	Round Cover UG-387/U-Mod	1.0mm Female	EAR99	PE-W10CA003	$5,287.99	See Web for Volume Pricing	20
			1.33:1		1.0mm Male	EAR99	PE-W10CA004	$5,210.00		21
WR-12	60-90		1.67:1	Round Cover UG-387/U	1.0mm Female	EAR99	PE-W12CA001	$3,348.39		22
					1.0mm Male	EAR99	PE-W12CA002	$5,111.72		23
WR-15	50-65	0.5	1.44:1	Round Cover UG-385/U	1.85mm Female	EAR99	PE-W15CA001	$1,517.58		24
					1.85mm Male	EAR99	PE-W15CA002	$1,563.51		25
WR-19	40-60	0.4	1.38:1	Round Cover UG-383/U-Mod	1.85mm Female	EAR99	PE-W19CA001	$1,631.35		26
					1.85mm Male	EAR99	PE-W19CA002	$1,461.16		27
WR-22	33-50		1.33:1	Round Cover UG-383/U	2.4mm Female	EAR99	PE-W22CA001	$1,691.47		28
					2.4mm Male	EAR99	PE-W22CA002	$1,405.68		29
			1.4:1		2.4mm Female	EAR99	PEW22CA100	$1,691.47		30
		0.5	1.6:1	UG383/U	2.4mm Female	EAR99	PEWCA1110	$1,528.61		31
WR-28	26.5-40	0.3	1.25:1	Square Cover UG-599/U	2.92mm Female	EAR99	PEWCA1078	$777.38		32
				UBR320	2.92mm Female	EAR99	PEWCA1103	$1,019.07		33
		0.4			2.92mm Female	EAR99	PEWCA1104	$847.96		34
		0.35	1.29:1	Square Cover UG-599/U	2.92mm Male	EAR99	PE-W28CA002	$838.20		35
			1.3:1		2.92mm Female	EAR99	PEWCA1000	$926.26		36
		0.3			2.92mm Female	EAR99	PEWCA1020	$777.69		37
		0.5		UBR320	2.92mm Female	EAR99	PEWCA1109	$1,102.74		38
			1.4:1	Square Cover	2.92mm Female	EAR99	PE9826	$518.00		39
WR-34	21.7-33	0.3	1.35:1	UBR260	2.92mm Female	EAR99	PEWCA1102	$1,019.07		40
	22-33		1.25:1	Square Cover UG-1530/U	2.92mm Female	EAR99	PEWCA1001	$765.94		41
		0.3			2.92mm Female	EAR99	PEWCA1021	$706.46		42
			1.4:1	Square Cover	2.92mm Female	EAR99	PE9827	$912.43		43
WR-42	17.6-26.7	0.3	1.25:1	UBR220	2.92mm Female	EAR99	PEWCA1101	$1,019.07		44
		0.5			SMA Female	EAR99	PEWCA1100	$418.28		45
	18-26.5		1.03:1	Square Cover UG-597/U	SMA Female	EAR99	PEWCA1026	$711.31		46
			1.25:1	Square Cover UG-595/U	SMA Female	EAR99	PEWCA1018	$801.97		47
		0.75		Square Cover UG-597/U	2.92mm Female	EAR99	PEWCA1019	$564.90		48
		0.3	1.29:1		2.92mm Female	EAR99	PE-W42CA001	$824.67		49
					2.92mm Male	EAR99	PE-W42CA002	$812.50		50
			1.3:1		2.92mm Female	EAR99	PEWCA1070	$944.03		51
		0.3			SMA Female	EAR99	PEWCA1022	$616.04		52
			1.4:1	Square Cover	2.92mm Female	EAR99	PE9878	$618.80		53
				Square Cover UG-597/U	2.92mm Male	EAR99	PE9813A	$660.15		54
				Square Type	2.92mm Female	EAR99	PE9812	$459.34		55
WR-51	14.5-22	0.3	1.25:1	UBR180	SMA Female	EAR99	PEWCA1099	$479.13		56
	15-22			Square Cover	SMA Female	EAR99	PEWCA1002A	$570.71		57
					SMA Female	EAR99	PEWCA1027	$795.98		58
			1.3:1	Square Type	SMA Female	EAR99	PE9828	$610.62		59
					SMA Female	EAR99	PE9879	$819.05		60
WR-62	11.9-18	0.2	1.25:1	UBR140	N Female	EAR99	PEWCA1097	$418.28		61

Waveguide to Coax Adapters

WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Flange Type	Connector	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
WR-62	11.9-18	0.2	1.25:1	UBR140	SMA Female	EAR99	PEWCA1098	$418.28	See Web for Volume Pricing			62
					SMA Female	EAR99	PEWCA1108	$471.51				63
	12.4-18		1.2:1	Square Cover UG-1665/U	SMA Male	EAR99	PE9809	$303.48				64
			1.25:1		N Female	EAR99	PEWCA1028	$702.17				65
		0.3			SMA Female	EAR99	PEWCA1023	$580.46				66
				Square Cover UG-419/U	SMA Female	EAR99	PEWCA1003	$538.33				67
			1.3:1	Square Cover UG-1665/U	N Female	EAR99	PEWCA1072	$917.73				68
					SMA Female	EAR99	PEWCA1071	$798.75				69
		0.3		Square Type	SMA Female	EAR99	PE9803	$381.14				70
			1.4:1	Square Cover	N Male	EAR99	PE9806	$669.56				71
				Square Type	N Female	EAR99	PE9866	$724.14				72
					N Female	EAR99	PE9875	$366.24				73
					SMA Female	EAR99	PE9846	$622.53				74
WR-75	10-15		1.25:1	Square Cover	N Female	EAR99	PEWCA1005	$720.90				75
					N Female	EAR99	PEWCA1029	$737.27				76
					SMA Female	EAR99	PEWCA1004	$658.63				77
		0.3			SMA Female	EAR99	PEWCA1024	$531.64				78
			1.3:1		N Female	EAR99	PEWCA1074	$886.14				79
					SMA Female	EAR99	PEWCA1073	$797.69				80
				Square Type	N Female	EAR99	PE9874	$466.93				81
					SMA Female	EAR99	PE9819	$368.09				82
			1.4:1		N Female	EAR99	PE9867	$734.06				83
					SMA Female	EAR99	PE9847	$677.32				84
	9.84-15	0.2	1.25:1	UBR120	N Female	EAR99	PEWCA1095	$418.28				85
					SMA Female	EAR99	PEWCA1096	$418.28				86
WR-90	8.2-12.4			CMR-90	N Female	EAR99	PEWCA1033	$830.13				87
					SMA Female	EAR99	PEWCA1032	$830.13				88
				CPR-90G	N Male	EAR99	PEWCA1035	$691.19				89
					N Female	EAR99	PEWCA1036	$748.99				90
					N Female	EAR99	PEWCA1009	$608.55				91
					SMA Female	EAR99	PEWCA1034	$690.83				92
					SMA Female	EAR99	PEWCA1007	$565.64				93
		0.25		Square Cover UG-135/U	N Female	EAR99	PE9868	$831.26				94
					N Female	EAR99	PEWCA1031	$838.86				95
					SMA Female	EAR99	PEWCA1075	$820.45				96
		0.3			SMA Female	EAR99	PEWCA1025	$538.33				97
					SMA Male	EAR99	PEWCA1030	$718.46				98
				Square Cover UG-39/U	N Female	EAR99	PEWCA1008	$702.85				99
					SMA Female	EAR99	PEWCA1006	$678.76				1
		0.2		UBR100	N Female	EAR99	PEWCA1092	$418.28				2
					SMA Female	EAR99	PEWCA1093	$418.28				3
					SMA Female	EAR99	PEWCA1107	$471.51				4
			1.3:1	CPR-90G	N Female	EAR99	PE9873	$486.75				5
				Square Type	N Female	EAR99	PE9801	$410.10				6
					N Male	EAR99	PE9889	$477.87				7
		0.3			SMA Female	EAR99	PE9804	$364.97				8
					SMA Male	EAR99	PE9810	$464.32				9
			1.4:1		SMA Female	EAR99	PE9848	$599.47				10
WR-102	7-10		1.25:1	Square Cover UG-1493/U	SMA Female	EAR99	PEWCA1037	$773.91				11
	7-11			Square Cover	N Female	EAR99	PE9869	$476.91				12
				Square Cover UG-1493/U	N Female	EAR99	PEWCA1038	$830.70				13
					N Male	EAR99	PEWCA1039	$830.70				14
					SMA Female	EAR99	PE9805	$666.38				15
			1.3:1	Square Cover	SMA Male	EAR99	PE9811	$352.21				16
				Square Type	N Female	EAR99	PE9802	$497.48				17
					N Male	EAR99	PE9890	$485.36				18
			1.4:1		SMA Female	EAR99	PE9871	$463.88				19
WR-112	6.57-9.99	0.2	1.25:1	UBR84	N Female	EAR99	PEWCA1089	$425.89				20
					SMA Female	EAR99	PEWCA1090	$419.08				21
					SMA Female	EAR99	PEWCA1106	$509.54				22

Waveguide to Coax Adapters

WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Flange Type	Connector	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
WR-112	7.05-10		1.25:1	CMR-112	N Female	EAR99	PEWCA1043	$741.18		See Web for Volume Pricing		23
					SMA Female	EAR99	PEWCA1042	$713.35				24
				CPR-112G	N Female	EAR99	PEWCA1045	$756.80				25
					N Female	EAR99	PEWCA1013	$593.23				26
					SMA Female	EAR99	PEWCA1044	$699.13				27
					SMA Female	EAR99	PEWCA1011	$693.84				28
				Square Cover UG-138/U	N Female	EAR99	PEWCA1041	$699.03				29
					SMA Female	EAR99	PEWCA1040	$755.59				30
				Square Cover UG-51/U	N Female	EAR99	PEWCA1012	$711.87				31
					SMA Female	EAR99	PEWCA1010	$720.90				32
			1.3:1	CPR-112G	N Female	EAR99	PE9837	$639.79				33
				Square Type	N Female	EAR99	PE9820	$410.56				34
					N Female	EAR99	PE9870	$593.41				35
					SMA Female	EAR99	PE9884	$375.16				36
			1.4:1		SMA Female	EAR99	PE9865	$643.58				37
WR-137	5.38-8.17	0.2	1.25:1	PDR70	N Female	EAR99	PEWCA1087	$492.33				38
				UDR70	N Female	EAR99	PEWCA1086	$438.30				39
					SMA Female	EAR99	PEWCA1088	$396.27				40
	5.85-8.2			CMR-137	N Female	EAR99	PEWCA1049	$732.13				41
					SMA Female	EAR99	PEWCA1048	$721.33				42
				CPR-137G	N Female	EAR99	PEWCA1051	$764.58				43
					N Female	EAR99	PEWCA1017	$604.50				44
					SMA Female	EAR99	PEWCA1050	$732.13				45
					SMA Female	EAR99	PEWCA1015	$624.15				46
				Round Cover UG-344/U	N Female	EAR99	PEWCA1016	$753.67				47
					SMA Female	EAR99	PEWCA1014	$624.15				48
				Round Cover UG-441/U	N Female	EAR99	PEWCA1047	$764.58				49
					SMA Female	EAR99	PEWCA1046	$732.13				50
			1.3:1	CMR-137	N Female	EAR99	PE9876	$229.32				51
		0.4			SMA Female	EAR99	PE9830	$539.07				52
				CPR-137G	N Female	EAR99	PE9838	$378.30				53
WR-159	4.9-7.05		1.25:1	CMR-159	N Female	EAR99	PEWCA1053	$673.87				54
					SMA Female	EAR99	PEWCA1052	$726.28				55
				CPR-159G	N Female	EAR99	PEWCA1055	$673.87				56
					SMA Female	EAR99	PEWCA1054	$699.03				57
			1.3:1	CMR-159	N Female	EAR99	PE9821	$728.12				58
					SMA Female	EAR99	PE9831	$673.53				59
				CPR-159G	N Female	EAR99	PE9839	$818.08				60
	5.38-8.17	0.2	1.25:1	UDR58	SMA Female	EAR99	PEWCA1085	$480.32				61
WR-187	3.94-5.99			PDR48	N Female	EAR99	PEWCA1084	$527.16				62
				UDR48	N Female	EAR99	PEWCA1083	$492.33				63
					N Female	EAR99	PEWCA1105	$551.37				64
					SMA Female	EAR99	PEWCA1076	$435.57				65
	3.95-5.85			CMR-187	N Female	EAR99	PEWCA1058	$581.96				66
					SMA Female	EAR99	PEWCA1057	$670.97				67
				CPR-187G	N Female	EAR99	PEWCA1059	$581.96				68
				Round Cover UG-407/U	N Female	EAR99	PEWCA1056	$709.99				69
			1.3:1	CMR-187	N Female	EAR99	PE9822	$490.87				70
					SMA Female	EAR99	PE9832	$882.24				71
				CPR-187G	N Female	EAR99	PE9840	$916.05				72
WR-229	3.3-4.9		1.25:1	CMR-229	N Female	EAR99	PEWCA1060	$692.60				73
				CPR-229G	N Female	EAR99	PEWCA1062	$692.60				74
					SMA Female	EAR99	PEWCA1061	$706.22				75
			1.3:1	CMR-229	N Female	EAR99	PE9823	$629.15				76
					SMA Female	EAR99	PE9833	$715.35				77
				CPR-229G	N Female	EAR99	PE9877	$974.03				78
WR-284	2.6-3.95		1.25:1	CMR-284	N Female	EAR99	PEWCA1064	$731.17				79
					SMA Female	EAR99	PE9834	$1,322.00				80
				CPR-284G	N Female	EAR99	PEWCA1065	$835.93				81
				Round Cover UG-584/U	N Female	EAR99	PEWCA1063	$1,035.66				82

Waveguide to Coax Adapters

WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Flange Type	Connector	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
WR-284	2.6-3.95	0.2	1.25:1	UDR32	N Female	EAR99	PEWCA1081	$638.82		See Web for Volume Pricing		83
					SMA Female	EAR99	PEWCA1082	$638.82				84
			1.3:1	CMR-284	N Female	EAR99	PE9824	$597.82				85
				CPR-284G	N Female	EAR99	PE9842	$571.82				86
WR-340	2.17-3.3	0.2	1.25:1	UDR26	N Female	EAR99	PEWCA1077	$653.89				87
	2.2-3.3			CPR-340F	N Female	EAR99	PEWCA1066	$1,404.15				88
				CPR-340G	N Female	EAR99	PEWCA1067	$1,383.44				89
WR-430	1.7-2.6			CPR-430F	N Female	EAR99	PEWCA1068	$1,571.22				90
				CPR-430G	N Female	EAR99	PEWCA1069	$1,620.34				91
			1.3:1	CPR-430F	N Female	EAR99	PE9872	$1,405.01				92
					SMA Female	EAR99	PE9835	$1,512.25				93
				CPR-430G	N Female	EAR99	PE9843	$1,604.79				94
	1.72-2.61	0.2	1.25:1	UDR22	N Female	EAR99	PEWCA1079	$1,188.79				95
		0.3			SMA Female	EAR99	PEWCA1080	$1,110.74				96

Double Ridge Waveguide to Coax Adapters

WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Flange Type	Connector	ECCN	Model No	1-4	5-9	10-24	25+	ROW
WRD-180	18-40	0.5	1.6:1	Square Cover UG	2.92mm Female	EAR99	PEWCA1120	$1,468.42	$1,395.00	$1,321.58	$1,262.84	97
				Square Cover	2.92mm Female	EAR99	PEWCA1115	$1,246.49	$1,184.17	$1,121.84	$1,071.98	98
WRD-650	6.5-18		1.5:1	Square Cover UG	N Female	EAR99	PEWCA1111	$904.19	$858.98	$813.77	$777.60	99
					N Female	EAR99	PEWCA1116	$1,323.18	$1,257.02	$1,190.86	$1,137.93	1
					SMA Female	EAR99	PEWCA1112	$957.44	$909.57	$861.70	$823.40	2
					SMA Female	EAR99	PEWCA1117	$1,323.18	$1,257.02	$1,190.86	$1,137.93	3
WRD-750	7.5-18				N Female	EAR99	PEWCA1113	$1,063.94	$1,010.74	$957.55	$914.99	4
					N Female	EAR99	PEWCA1118	$1,323.18	$1,257.02	$1,190.86	$1,137.93	5
					SMA Female	EAR99	PEWCA1114	$1,194.09	$1,134.39	$1,074.68	$1,026.92	6
					SMA Female	EAR99	PEWCA1119	$1,323.18	$1,257.02	$1,190.86	$1,137.93	7

Corner Reflectors

Description	Model No	1	2-4	5-9	10+	ROW
1.4 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0000	$940.63	$907.71	$874.79	$846.57	8
1.8 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0001	$1,034.69	$998.48	$962.26	$931.22	9
2.4 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0002	$1,128.75	$1,089.24	$1,049.74	$1,015.88	10
3.2 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0003	$1,582.09	$1,526.72	$1,471.34	$1,423.88	11
4.3 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0004	$1,558.75	$1,504.19	$1,449.64	$1,402.88	12
6 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0005	$1,854.38	$1,789.48	$1,724.57	$1,668.94	13
8 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0006	$2,203.75	$2,126.62	$2,049.49	$1,983.38	14
8.5 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0007	$2,526.25	$2,437.83	$2,349.41	$2,273.63	15

Corner Reflectors

Description	Model No	1	2-4	5-9	10+	ROW
8.9 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0008	$2,821.88	$2,723.11	$2,624.35	$2,539.69	16
10 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0009	$3,359.38	$3,241.80	$3,124.22	$3,023.44	17
13 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0010	$3,896.88	$3,760.49	$3,624.10	$3,507.19	18
13.5 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0011	$4,434.38	$4,279.18	$4,123.97	$3,990.94	19
16 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0012	$6,450.00	$6,224.25	$5,998.50	$5,805.00	20
24 inch Edge Length, Trihedral Corner Reflector, ¼-20 Threaded Hole Mount, Aluminum Body, Gold Chem Film Finish	PEWRL0013	$8,868.75	$8,558.34	$8,247.94	$7,981.88	21

WAVEGUIDE BANDPASS FILTERS

Waveguide Type	RF Frequency (GHz.)	Max VSWR	Flange Type	ECCN	Model No	1-9	10-24	25-49	50+	ROW
WR-28	30 - 31	1.4:1	Square Cover	EAR99	PE-W28F001	$396.26	$376.45	$356.63	$340.78	22
	38 - 40	1.5:1		EAR99	PE-W28F002	$409.60	$389.12	$368.64	$352.26	23
WR-42	20.2 - 21.2	1.5:1		EAR99	PE-W42F001	$407.32	$386.95	$366.59	$350.30	24
	24.25 - 24.45	1.8:1		EAR99	PE-W42F002	$380.36	$365.15	$353.73	$346.13	25
		1.5:1		EAR99	PE-W42F004	$397.91	$378.01	$358.12	$342.20	26

WAVEGUIDE BENDS

Waveguide Type	RF Frequency (GHz.)	Insertion Loss (dB)	Bend Plane	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-5	140 - 220	0	E-Bend	Round Cover UG-383/U-Mod	EAR99	PEW5B0000	$571.82	See Web for Volume Pricing	27
			H-Bend		EAR99	PEW5B0001	$563.39		28
WR-6	110 - 170	0.35	E-Bend		EAR99	PEW6B0000	$539.40		29
			H-Bend		EAR99	PEW6B0001	$539.40		30
WR-8	90 - 140	0.3	E-Bend		EAR99	PEW8B0000	$539.40		31
			H-Bend		EAR99	PEW8B0001	$531.44		32
WR-10	75 - 110	0.21	E-Bend	Round Cover UG-387/U-Mod	EAR99	PE-W10B001	$525.93		33
			H-Bend		EAR99	PE-W10B002	$525.93		34
WR-12	60 - 90		E-Bend	Round Cover UG-387/U	EAR99	PE-W12B001	$443.11		35
			H-Bend		EAR99	PE-W12B002	$430.69		36
WR-15	50 - 75	0.17	E-Bend	Round Cover UG-385/U	EAR99	PE-W15B001	$583.98		37
			H-Bend		EAR99	PE-W15B002	$583.98		38
WR-19	40 - 60	0.18	E-Bend	Round Cover UG-383/U-Mod	EAR99	PE-W19B001	$420.58		39
			H-Bend		EAR99	PE-W19B002	$420.58		40
WR-22	33 - 50	0.16	E-Bend	Round Cover UG-383/U	EAR99	PE-W22B001	$420.58		41
		0.25	H-Bend		EAR99	PEW22B100	$398.85		42
			E-Bend		EAR99	PEW22B101	$398.85		43
WR-28	26.5 - 40	0.28		Square Cover UG-599/U	EAR99	PE-W28B001	$450.04		44
			H-Bend		EAR99	PE-W28B002	$560.44		45
		0.3	E-Bend		EAR99	PE-W28B003	$464.81		46

See Our Website For Current Pricing & Real-Time Stock Availability!

Waveguides

WAVEGUIDE BENDS

Waveguide Type	RF Frequency (GHz.)	Insertion Loss (dB)	Bend Plane	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-42	18 - 26.5	0.15	H-Bend	Square Cover UG-595/U	EAR99	PEW42B100	$433.14	See Web for Volume Pricing	47
		0.2	E-Bend		EAR99	PEW42B101	$443.40		48
WR-51	15 - 22	0.09		UBR180	EAR99	PE-W51B001	$409.60		49
WR-62	12.4 - 18			Square Cover UG-419/U	EAR99	PE-W62B003	$409.60		50
			H-Bend		EAR99	PE-W62B004	$438.27		51
		0.15	E-Bend		EAR99	PE-W62B001	$455.47		52
			H-Bend		EAR99	PE-W62B002	$421.36		53
WR-75	10 - 15		E-Bend	UBR120	EAR99	PE-W75B001	$462.43		54
			H-Bend		EAR99	PE-W75B002	$498.91		55
WR-90	8.2 - 12.4		E-Bend	Square Cover UG-39/U	EAR99	PE-W90B001	$423.85		56
			H-Bend		EAR99	PE-W90B002	$433.35		57
			E-Bend	CPR-90G	EAR99	PE-W90B003A	$424.94		58
			H-Bend		EAR99	PE-W90B004A	$372.16		59
WR-112	7.05 - 10		E-Bend	Square Cover UG-51/U	EAR99	PE-W112B001	$615.39		60
			H-Bend		EAR99	PE-W112B002	$521.91		61
WR-137	5.85 - 8.2		E-Bend	Round Cover UG-344/U	EAR99	PE-W137B001	$443.90		62
			H-Bend		EAR99	PE-W137B002	$468.13		63
			E-Bend	CPR-137G	EAR99	PE-W137B003A	$548.21		64
			H-Bend		EAR99	PE-W137B004	$540.12		65
WRD-180	18 - 40	0.4	E-Bend	Square Cover UG	EAR99	PEWRD180B001	$742.28		66
			H-Bend		EAR99	PEWRD180B002	$742.28		67
WRD-650	6.5 - 18		E-Bend		EAR99	PEWRD650B001	$661.59		68
			H-Bend		EAR99	PEWRD650B002	$661.59		69
WRD-750	7.5 - 18		E-Bend		EAR99	PEWRD750B001	$661.59		70
			H-Bend		EAR99	PEWRD750B002	$661.59		71

WAVEGUIDE BULKHEAD ADAPTERS

Frequency Range (GHz.)	Waveguide Size	Flange 1	Flange 2	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
75.0 - 110.0	WR-10	Round Cover UG-387/U-Mod	Round Cover UG-387/ U-Mod	PEWAD5000	$1,112.30	See Web for Volume Pricing	72
60.0 - 90.0	WR-12	Round Cover UG-387/U	Round Cover UG-387/U	PEWAD5001	$1,006.21		73
50.0 - 75.0	WR-15	Round Cover UG-385/U	Round Cover UG-385/U	PEWAD5002	$1,006.21		74
40.0 - 60.0	WR-19	Round Cover UG-383/U-Mod	Round Cover UG-383/ U-Mod	PEWAD5003	$991.36		75
33.0 - 50.0	WR-22	Round Cover UG-383/U	Round Cover UG-383/U	PEWAD5007A	$924.78		76
			Round Cover UG-383/U	PEWAD5004	$991.36		77
26.5 - 40.0	WR-28	Square Cover UG-599/U	Square Cover UG-599/U	PEWAD5008	$803.46		78
			Square Cover UG-599/U	PEWAD5005	$1,126.96		79
22.0 - 33.0	WR-34	Square Cover UG-1530/U	Square Cover UG-1530/U	PEWAD5009	$818.50		80
18.0 - 26.5	WR-42	Square Cover UG-595/U	Square Cover UG-595/U	PEWAD5010	$841.02		81
			Square Cover UG-595/U	PEWAD5006	$1,126.96		82
15.0 - 22.0	WR-51	Square Cover	Square Cover	PEWAD5011	$843.40		83
12.4 - 18.0	WR-62	Square Cover UG-1665/U	Square Cover UG-1665/U	PEWAD5012	$893.57		84
10.0 - 15.0	WR-75	Square Cover	Square Cover	PEWAD5013	$919.87		85
8.2 - 12.4	WR-90	Square Cover UG-39/U	Square Cover UG-39/U	PEWAD5014	$953.66		86
		CPR-90G	CPR-90G	PEWAD5015	$953.66		87
7.05 - 10.0	WR-112	Square Cover UG-51/U	Square Cover UG-51/U	PEWAD5016	$991.36		88
		CPR-112G	CPR-112G	PEWAD5017	$1,006.21		89
5.85 - 8.2	WR-137	Square Cover UG-344/U	Square Cover UG-344/U	PEWAD5018	$1,058.77		90
		CPR-137G	CPR-137G	PEWAD5019	$1,058.77		91

WAVEGUIDE CONVERTER MIXERS

Down Converter

RF/LO Frequency (GHz.)	IF Frequency (GHz.)	LO Power (dBm)	Typ Conv. Loss (dB)	RF & LO Waveguide Type	IF Connector	ECCN	Model No	1	2-4	5-9	10+	ROW
26.5 - 40	DC - 18	15	6	WR-28 UG-599/U	SMA Female	EAR99	PE12D1005	$3,834.26	$3,680.89	$3,527.52	$3,374.15	92
33 - 50	DC - 18	15	7	WR-22 UG-383/U	SMA Female	EAR99	PE12D1004	$4,417.94	$4,241.22	$4,064.50	$3,887.79	93
50 - 75	DC - 18	15	8	WR-15 UG-385/U	SMA Female	EAR99	PE12D1002	$4,984.84	$4,785.45	$4,586.05	$4,386.66	94
60 - 90	DC - 18	15	9	WR-12 UG-387/U	SMA Female	EAR99	PE12D1001	$4,638.43	$4,452.89	$4,267.36	$4,081.82	95
75 - 110	DC - 18	15	9	WR-10 UG-387/U-Mod	SMA Female	EAR99	PE12D1000	$6,521.71	$6,260.84	$5,999.97	$5,739.10	96

Up Converter

RF/LO Frequency (GHz.)	IF Frequency (GHz.)	LO Power (dBm)	Typ Conv. Loss (dB)	RF & LO Waveguide Type	IF Connector	ECCN	Model No	1	2-4	5-9	10+	ROW
26.5 - 40	DC - 18	15	6	WR-28 UG-599/U	SMA Female	EAR99	PE13U1005	$4,151.05	$3,985.01	$3,818.97	$3,652.92	97
33 - 50	DC - 18	15	7	WR-22 UG-383/U	SMA Female	EAR99	PE13U1004	$5,023.61	$4,822.67	$4,621.72	$4,420.78	98
40 - 60	DC - 18	15	7	WR-19 UG-383/U	SMA Female	EAR99	PE13U1003	$5,194.53	$4,986.75	$4,778.97	$4,571.19	99
50 - 75	DC - 18	15	8	WR-15 UG-385/U	SMA Female	EAR99	PE13U1002	$5,983.77	$5,744.42	$5,505.07	$5,265.72	1
60 - 90	DC - 18	15	9	WR-12 UG-387/U	SMA Female	EAR99	PE13U1001	$5,540.23	$5,318.62	$5,097.01	$4,875.40	2
75 - 110	DC - 18	15	9	WR-10 UG-387/U	SMA Female	EAR99	PE13U1000	$5,579.55	$5,356.37	$5,133.19	$4,910.00	3

WAVEGUIDE COUPLERS

Broadwall

WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Coupling (dB)	Directivity (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-10	75 - 110	1.1	1.2:1	20	30	Round Cover UG-387/U-Mod	EAR99	PE-W10CP001-20	$2,520.34	$2,419.53	$2,318.71	$2,217.90	4
				20	30		EAR99	PE-W10CP003-20	$2,797.74	$2,685.83	$2,573.92	$2,462.01	5
		1.4		10	30		EAR99	PE-W10CP001-10	$2,520.34	$2,419.53	$2,318.71	$2,217.90	6
				10	30		EAR99	PE-W10CP003-10	$2,797.74	$2,685.83	$2,573.92	$2,462.01	7
			1.1:1	20	40	Round Cover UG-387/U	EAR99	PEW10CP010-20	$2,653.00	$2,546.88	$2,440.76	$2,334.64	8
WR-12	60 - 90	1	1.2:1	20	30		EAR99	PE-W12CP001-20	$2,682.26	$2,574.97	$2,467.68	$2,360.39	9
				20	30		EAR99	PE-W12CP003-20	$2,714.84	$2,606.25	$2,497.65	$2,389.06	10
		1.4		10	30		EAR99	PE-W12CP001-10	$2,682.26	$2,574.97	$2,467.68	$2,360.39	11
				10	30		EAR99	PE-W12CP003-10	$2,823.43	$2,710.49	$2,597.56	$2,484.62	12
WR-15	50 - 75	1	1.1:1	20	40	Round Cover UG-385/U	EAR99	PEWCP1080-20	$2,515.43	$2,414.81	$2,314.20	$2,213.58	13
			1.2:1	20	30		EAR99	PE-W15CP001-20	$2,613.53	$2,508.99	$2,404.45	$2,299.91	14
		1.4		10	30		EAR99	PE-W15CP001-10	$2,528.32	$2,427.19	$2,326.05	$2,224.92	15
				10	30		EAR99	PE-W15CP003-10	$2,528.32	$2,427.19	$2,326.05	$2,224.92	16
WR-19	40 - 60	0.8		10	30	Round Cover UG-383/U	EAR99	PE-W19CP003-10	$2,642.30	$2,536.61	$2,430.92	$2,325.22	17
				20	30		EAR99	PE-W19CP003-20	$2,590.49	$2,486.87	$2,383.25	$2,279.63	18
		1		20	30		EAR99	PE-W19CP001-20	$2,333.65	$2,240.30	$2,146.96	$2,053.61	19
		1.4		10	30		EAR99	PE-W19CP001-10	$2,333.65	$2,240.30	$2,146.96	$2,053.61	20
WR-22	33 - 50	0.8	1.1:1	20	30		EAR99	PEW22CP010-20	$2,397.79	$2,301.88	$2,205.97	$2,110.06	21
			1.2:1	20	30		EAR99	PE-W22CP003-20	$2,629.47	$2,524.29	$2,419.11	$2,313.93	22
		1	1.05:1	10			EAR99	PEWCP1079-10	$2,491.03	$2,391.39	$2,291.75	$2,192.11	23
		1.2	1.2:1	10	30		EAR99	PE-W22CP001-10	$2,528.32	$2,427.19	$2,326.05	$2,224.92	24

Broadwall

WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Coupling (dB)	Directivity (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-28	26.5 - 40	0.6	1.1:1	20	30	Square Cover UG-599/U	EAR99	PEW28CP010-20	$2,445.43	$2,347.61	$2,249.80	$2,151.98	25
		0.7	1.05:1	20	40		EAR99	PE-W28CP002-20	$2,445.43	$2,347.61	$2,249.80	$2,151.98	26
			1.2:1	10	30		EAR99	PE-W28CP003-10	$2,543.25	$2,441.52	$2,339.79	$2,238.06	27
		1		10	30		EAR99	PE-W28CP002-10	$2,445.43	$2,347.61	$2,249.80	$2,151.98	28
WR-34	22 - 33	0.15	1.05:1	20	35	Square Cover UG-1530/U	EAR99	PEWCP1006	$1,645.92	$1,580.08	$1,514.25	$1,448.41	29
				30	35		EAR99	PEWCP1007	$1,645.92	$1,580.08	$1,514.25	$1,448.41	30
		0.35		10	35		EAR99	PEWCP1005	$1,584.14	$1,520.77	$1,457.41	$1,394.04	31
WR-42	18 - 26.5	0.6	1.2:1	20	30	Square Cover UG-595/U	EAR99	PE-W42CP002-20	$2,445.43	$2,347.61	$2,249.80	$2,151.98	32
				20	30		EAR99	PE-W42CP004-20	$2,505.73	$2,405.50	$2,305.27	$2,205.04	33
		1		10	30		EAR99	PE-W42CP004-10	$2,505.73	$2,405.50	$2,305.27	$2,205.04	34
WR-51	15 - 22	0.15	1.05:1	10	35	Square Cover	EAR99	PEWCP1008	$1,614.41	$1,549.83	$1,485.26	$1,420.68	35
				20	35		EAR99	PEWCP1009	$1,614.41	$1,549.83	$1,485.26	$1,420.68	36
				30	35		EAR99	PEWCP1010	$1,678.98	$1,611.82	$1,544.66	$1,477.50	37
WR-62	12.4 - 18			10	40	Square Cover UG-419/U	EAR99	PEWCP1011	$1,441.15	$1,383.50	$1,325.86	$1,268.21	38
				20	40		EAR99	PEWCP1012	$1,498.79	$1,438.84	$1,378.89	$1,318.94	39
				30	40		EAR99	PEWCP1013	$1,498.79	$1,438.84	$1,378.89	$1,318.94	40
WR-75	10 - 15			10	40	Square Cover	EAR99	PEWCP1014	$1,388.99	$1,333.43	$1,277.87	$1,222.31	41
				20	40		EAR99	PEWCP1015	$1,388.99	$1,333.43	$1,277.87	$1,222.31	42
				30	40		EAR99	PEWCP1016	$1,523.37	$1,462.44	$1,401.50	$1,340.57	43
WR-90	8.2 - 12.4			10	40	Square Cover UG-39/U	EAR99	PEWCP1017	$1,687.17	$1,619.68	$1,552.20	$1,484.71	44
				10	40	CPR-90G	EAR99	PEWCP1020	$1,545.81	$1,483.98	$1,422.15	$1,360.31	45
				20	40	Square Cover UG-39/U	EAR99	PEWCP1018	$1,622.29	$1,557.40	$1,492.51	$1,427.62	46
				20	40	CPR-90G	EAR99	PEWCP1021	$1,545.81	$1,483.98	$1,422.15	$1,360.31	47
				30	40	Square Cover UG-39/U	EAR99	PEWCP1019	$1,687.17	$1,619.68	$1,552.20	$1,484.71	48
				30	40	CPR-90G	EAR99	PEWCP1022	$1,568.96	$1,506.20	$1,443.44	$1,380.68	49
WR-112	7.05 - 10			10	40	Square Cover UG-51/U	EAR99	PEWCP1023A	$1,500.67	$1,440.64	$1,380.62	$1,320.59	50
				10	40	CPR-112G	EAR99	PEWCP1026	$1,471.15	$1,412.30	$1,353.46	$1,294.61	51
				20	40	Square Cover UG-51/U	EAR99	PEWCP1024	$1,418.88	$1,362.12	$1,305.37	$1,248.61	52
				20	40	CPR-112G	EAR99	PEWCP1027	$1,471.15	$1,412.30	$1,353.46	$1,294.61	53
				30	40	Square Cover UG-51/U	EAR99	PEWCP1025	$1,496.29	$1,436.44	$1,376.59	$1,316.74	54
				30	40	CPR-112G	EAR99	PEWCP1028	$1,471.15	$1,412.30	$1,353.46	$1,294.61	55
WR-137	5.85 - 8.2			10	40	Round Cover UG-344/U	EAR99	PEWCP1029	$1,501.01	$1,440.97	$1,380.93	$1,320.89	56
				10	40	CPR-137G	EAR99	PEWCP1032	$1,576.55	$1,513.49	$1,450.43	$1,387.36	57
				20	40	Round Cover UG-344/U	EAR99	PEWCP1030	$1,501.01	$1,440.97	$1,380.93	$1,320.89	58
				20	40	CPR-137G	EAR99	PEWCP1033	$1,553.29	$1,491.16	$1,429.03	$1,366.90	59
				30	40	Round Cover UG-344/U	EAR99	PEWCP1031	$1,501.01	$1,440.97	$1,380.93	$1,320.89	60
				30	40	CPR-137G	EAR99	PEWCP1034	$1,638.04	$1,572.52	$1,507.00	$1,441.48	61

Crossguide*

WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Coupling (dB)	Directivity (dB)	Flange Type	ECCN	Model No	1-4	5-9	10-24	25+	ROW
WR-34	22 - 33	0.1	1.05:1	20	20	Square Cover UG-1530/U	EAR99	PEWCP1035	$1,050.83	$998.29	$945.75	$903.71	62
				30	20		EAR99	PEWCP1036	$1,094.80	$1,040.06	$985.32	$941.53	63
				40	25		EAR99	PEWCP1037	$1,066.57	$1,013.24	$959.91	$917.25	64
				50	10		EAR99	PEWCP1038	$1,050.83	$998.29	$945.75	$903.71	65
WR-42	18 - 26.5			20	30	Square Cover UG-595/U	EAR99	PEWCP1039	$850.01	$807.51	$765.01	$731.01	66
				30	20		EAR99	PEWCP1040	$918.48	$872.56	$826.63	$789.89	67
				40	20		EAR99	PEWCP1041	$837.46	$795.59	$753.71	$720.22	68
				50	10		EAR99	PEWCP1042	$918.48	$872.56	$826.63	$789.89	69

*These WG crossguide couplers are available as assemblies with termination and/or with WG to Coax Adapters, see WG Coupler Asemblies or visit our website

Crossguide*

WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Coupling (dB)	Directivity (dB)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
WR-51	15 - 22	0.1	1.05:1	20	20	Square Cover	EAR99	PEWCP1043	$1,293.51	See Web for Volume Pricing			70
				30	30		EAR99	PEWCP1044	$1,293.51				71
				40	30		EAR99	PEWCP1045	$1,293.51				72
				50	10		EAR99	PEWCP1046	$1,293.51				73
WR-62	12.4 - 18			20	20	Square Cover UG-419/U	EAR99	PEWCP1047	$883.15				74
				30	10		EAR99	PEWCP1048	$883.15				75
				40	30		EAR99	PEWCP1049	$837.46				76
				50	10		EAR99	PEWCP1050	$837.46				77
WR-75	10 - 15			50	10	Square Cover	EAR99	PEWCP1054	$842.78				78
				20	25		EAR99	PEWCP1051	$875.66				79
				30	25		EAR99	PEWCP1052A	$868.91				80
				40	15		EAR99	PEWCP1053	$888.77				81
WR-90	8.2 - 12.4			20	20	Square Cover UG-39/U	EAR99	PEWCP1055	$793.93				82
				20	25	CPR-90G	EAR99	PEWCP1059	$880.12				83
				30	20	Square Cover UG-39/U	EAR99	PEWCP1056	$833.74				84
				30	20	CPR-90G	EAR99	PEWCP1060	$880.12				85
				40	10	Square Cover UG-39/U	EAR99	PEWCP1057	$900.92				86
				40	10	CPR-90G	EAR99	PEWCP1061	$880.12				87
				50	10	Square Cover UG-39/U	EAR99	PEWCP1058	$900.92				88
				50	10	CPR-90G	EAR99	PEWCP1062	$951.03				89
WR-112	7.05 - 10			20	45	Square Cover UG-51/U	EAR99	PEWCP1063	$959.04				90
				20	25	CPR-112G	EAR99	PEWCP1067	$954.80				91
				30	25	Square Cover UG-51/U	EAR99	PEWCP1064	$996.45				92
				30	25	CPR-112G	EAR99	PEWCP1068	$969.10				93
				40	20	Square Cover UG-51/U	EAR99	PEWCP1065	$944.90				94
				40	20	CPR-112G	EAR99	PEWCP1069	$954.80				95
				50	10	Square Cover UG-51/U	EAR99	PEWCP1066	$1,036.32				96
				50	10	CPR-112G	EAR99	PEWCP1070	$1,047.18				97
WR-137	5.85 - 8.2			20	25	Round Cover UG-344/U	EAR99	PEWCP1071	$960.13				98
				20	20	CPR-137G	EAR99	PEWCP1075	$917.47				99
				30	20	Round Cover UG-344/U	EAR99	PEWCP1072	$960.13				1
				30	20	CPR-137G	EAR99	PEWCP1076	$931.21				2
				40	20	Round Cover UG-344/U	EAR99	PEWCP1073	$960.13				3
				40	20	CPR-137G	EAR99	PEWCP1077	$917.47				4
				50	10	Round Cover UG-344/U	EAR99	PEWCP1074	$960.13				5
				50	10	CPR-137G	EAR99	PEWCP1078	$917.47				6

Crossguide* with Termination

WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Coupling (dB)	Directivity (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-34	22 - 33	0.1	1.05:1	20	20	Square Cover UG-1530/U	EAR99	PEWCT1000	$1,657.10	$1,590.82	$1,524.53	$1,458.25	7
				30	20		EAR99	PEWCT1001	$1,657.10	$1,590.82	$1,524.53	$1,458.25	8
				40	25		EAR99	PEWCT1002	$1,747.50	$1,677.60	$1,607.70	$1,537.80	9
				50	10		EAR99	PEWCT1003	$1,657.10	$1,590.82	$1,524.53	$1,458.25	10
WR-42	18 - 26.5			20	30	Square Cover UG-595/U	EAR99	PEWCT1004	$1,410.66	$1,354.23	$1,297.81	$1,241.38	11
				30	20		EAR99	PEWCT1005	$1,410.66	$1,354.23	$1,297.81	$1,241.38	12
				40	20		EAR99	PEWCT1006	$1,410.66	$1,354.23	$1,297.81	$1,241.38	13
				50	10		EAR99	PEWCT1007	$1,410.66	$1,354.23	$1,297.81	$1,241.38	14

*These WG crossguide couplers are available as assemblies with termination and/or with WG to Coax Adapters, see WG Coupler Asemblies or visit our website

Crossguide* with Termination

WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Coupling (dB)	Directivity (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-51	15 - 22	0.1	1.05:1	20	20	Square Cover	EAR99	PEWCT1008	$1,880.01	$1,804.81	$1,729.61	$1,654.41	15
				30	30		EAR99	PEWCT1009	$1,880.01	$1,804.81	$1,729.61	$1,654.41	16
				40	30		EAR99	PEWCT1010	$1,880.01	$1,804.81	$1,729.61	$1,654.41	17
				50	10		EAR99	PEWCT1011	$1,880.01	$1,804.81	$1,729.61	$1,654.41	18
WR-62	12.4 - 18			20	20	Square Cover UG-419/U	EAR99	PEWCT1012	$1,395.72	$1,339.89	$1,284.06	$1,228.23	19
				30	10		EAR99	PEWCT1013	$1,471.87	$1,413.00	$1,354.12	$1,295.25	20
				40	30		EAR99	PEWCT1014	$1,395.72	$1,339.89	$1,284.06	$1,228.23	21
				50	10		EAR99	PEWCT1015	$1,395.72	$1,339.89	$1,284.06	$1,228.23	22
WR-75	10 - 15			50	10	Square Cover	EAR99	PEWCT1019	$1,481.31	$1,422.06	$1,362.81	$1,303.55	23
				20	25		EAR99	PEWCT1016	$1,481.31	$1,422.06	$1,362.81	$1,303.55	24
				30	25		EAR99	PEWCT1017	$1,404.68	$1,348.49	$1,292.31	$1,236.12	25
				40	15		EAR99	PEWCT1018	$1,404.68	$1,348.49	$1,292.31	$1,236.12	26
WR-90	8.2 - 12.4			20	20	Square Cover UG-39/U	EAR99	PEWCT1020	$1,372.58	$1,317.68	$1,262.77	$1,207.87	27
				20	25	CPR-90G	EAR99	PEWCT1024	$1,441.28	$1,383.63	$1,325.98	$1,268.33	28
				30	20	Square Cover UG-39/U	EAR99	PEWCT1021	$1,372.58	$1,317.68	$1,262.77	$1,207.87	29
				30	20	CPR-90G	EAR99	PEWCT1025	$1,441.28	$1,383.63	$1,325.98	$1,268.33	30
				40	10	Square Cover UG-39/U	EAR99	PEWCT1022	$1,372.58	$1,317.68	$1,262.77	$1,207.87	31
				40	10	CPR-90G	EAR99	PEWCT1026	$1,441.28	$1,383.63	$1,325.98	$1,268.33	32
				50	10	Square Cover UG-39/U	EAR99	PEWCT1023	$1,393.13	$1,337.40	$1,281.68	$1,225.95	33
				50	10	CPR-90G	EAR99	PEWCT1027	$1,441.28	$1,383.63	$1,325.98	$1,268.33	34
WR-112	7.05 - 10			20	45	Square Cover UG-51/U	EAR99	PEWCT1028	$1,530.89	$1,469.65	$1,408.42	$1,347.18	35
				20	25	CPR-112G	EAR99	PEWCT1032	$1,548.06	$1,486.14	$1,424.22	$1,362.29	36
				30	25	Square Cover UG-51/U	EAR99	PEWCT1029	$1,616.39	$1,551.73	$1,487.08	$1,422.42	37
				30	25	CPR-112G	EAR99	PEWCT1033	$1,548.06	$1,486.14	$1,424.22	$1,362.29	38
				40	20	Square Cover UG-51/U	EAR99	PEWCT1030	$1,532.76	$1,471.45	$1,410.14	$1,348.83	39
				40	20	CPR-112G	EAR99	PEWCT1034	$1,548.06	$1,486.14	$1,424.22	$1,362.29	40
				50	10	Square Cover UG-51/U	EAR99	PEWCT1031	$1,532.76	$1,471.45	$1,410.14	$1,348.83	41
				50	10	CPR-112G	EAR99	PEWCT1035	$1,548.06	$1,486.14	$1,424.22	$1,362.29	42
WR-137	5.85 - 8.2			20	25	Round Cover UG-344/U	EAR99	PEWCT1036	$1,579.42	$1,516.24	$1,453.07	$1,389.89	43
				20	20	CPR-137G	EAR99	PEWCT1040	$1,541.34	$1,479.69	$1,418.03	$1,356.38	44
				30	20	Round Cover UG-344/U	EAR99	PEWCT1037	$1,579.42	$1,516.24	$1,453.07	$1,389.89	45
				30	20	CPR-137G	EAR99	PEWCT1041	$1,541.34	$1,479.69	$1,418.03	$1,356.38	46
				40	20	Round Cover UG-344/U	EAR99	PEWCT1038	$1,579.42	$1,516.24	$1,453.07	$1,389.89	47
				40	20	CPR-137G	EAR99	PEWCT1042	$1,541.34	$1,479.69	$1,418.03	$1,356.38	48
				50	10	Round Cover UG-344/U	EAR99	PEWCT1039	$1,579.42	$1,516.24	$1,453.07	$1,389.89	49
				50	10	CPR-137G	EAR99	PEWCT1043	$1,541.34	$1,479.69	$1,418.03	$1,356.38	50

Crossguide* with Termination and WG to Coax Adapter

WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Coupling (dB)	Directivity (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-34	22 - 33	0.1	1.05:1	20	20	Square Cover UG-1530/U	EAR99	PEWCT1044	$2,312.87	$2,220.36	$2,127.84	$2,035.33	51
				30	20		EAR99	PEWCT1045	$2,347.49	$2,253.59	$2,159.69	$2,065.79	52
				40	25		EAR99	PEWCT1046	$2,312.87	$2,220.36	$2,127.84	$2,035.33	53
				50	10		EAR99	PEWCT1047	$2,312.87	$2,220.36	$2,127.84	$2,035.33	54
WR-42	18 - 26.5			20	30	Square Cover UG-595/U	EAR99	PEWCT1048	$2,092.03	$2,008.35	$1,924.67	$1,840.99	55
				30	20		EAR99	PEWCT1049	$2,123.36	$2,038.43	$1,953.49	$1,868.56	56
				40	20		EAR99	PEWCT1050	$2,092.03	$2,008.35	$1,924.67	$1,840.99	57
				50	10		EAR99	PEWCT1051	$2,092.03	$2,008.35	$1,924.67	$1,840.99	58

*These WG crossguide couplers are available as assemblies with termination and/or with WG to Coax Adapters, see WG Coupler Asemblies or visit our website

Crossguide* with Termination and WG to Coax Adapter

WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Coupling (dB)	Directivity (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-51	15 - 22	0.1	1.05:1	20	20	Square Cover	EAR99	PEWCT1052	$2,473.42	$2,374.48	$2,275.55	$2,176.61	59
				30	30		EAR99	PEWCT1053	$2,473.42	$2,374.48	$2,275.55	$2,176.61	60
				40	30		EAR99	PEWCT1054	$2,473.42	$2,374.48	$2,275.55	$2,176.61	61
				50	10		EAR99	PEWCT1055	$2,473.42	$2,374.48	$2,275.55	$2,176.61	62
WR-62	12.4 - 18			20	20	Square Cover UG-419/U	EAR99	PEWCT1056	$1,956.59	$1,878.33	$1,800.06	$1,721.80	63
				30	10		EAR99	PEWCT1057	$2,114.21	$2,029.64	$1,945.07	$1,860.50	64
				40	30		EAR99	PEWCT1058	$1,927.73	$1,850.62	$1,773.51	$1,696.40	65
				50	10		EAR99	PEWCT1059	$1,956.59	$1,878.33	$1,800.06	$1,721.80	66
WR-75	10 - 15			40	15	Square Cover	EAR99	PEWCT1066	$2,189.68	$2,102.09	$2,014.51	$1,926.92	67
				50	10		EAR99	PEWCT1063	$2,091.37	$2,007.72	$1,924.06	$1,840.41	68
				50	10		EAR99	PEWCT1067	$2,026.43	$1,945.37	$1,864.32	$1,783.26	69
				20	25		EAR99	PEWCT1060	$1,944.28	$1,866.51	$1,788.74	$1,710.97	70
				20	25		EAR99	PEWCT1064	$2,026.43	$1,945.37	$1,864.32	$1,783.26	71
				30	25		EAR99	PEWCT1061	$2,050.35	$1,968.34	$1,886.32	$1,804.31	72
				30	25		EAR99	PEWCT1065	$1,996.54	$1,916.68	$1,836.82	$1,756.96	73
				40	15		EAR99	PEWCT1062	$2,132.37	$2,047.08	$1,961.78	$1,876.49	74
WR-90	8.2 - 12.4			20	20	Square Cover UG-39/U	EAR99	PEWCT1068	$2,035.70	$1,954.27	$1,872.84	$1,791.42	75
				20	25	CPR-90G	EAR99	PEWCT1072	$2,000.27	$1,920.26	$1,840.25	$1,760.24	76
				20	20	Square Cover UG-39/U	EAR99	PEWCT1076	$2,162.18	$2,075.69	$1,989.21	$1,902.72	77
				20	25	CPR-90G	EAR99	PEWCT1080	$2,071.91	$1,989.03	$1,906.16	$1,823.28	78
				30	20	Square Cover UG-39/U	EAR99	PEWCT1069	$2,035.70	$1,954.27	$1,872.84	$1,791.42	79
				30	20	CPR-90G	EAR99	PEWCT1073	$2,000.27	$1,920.26	$1,840.25	$1,760.24	80
				30	20	Square Cover UG-39/U	EAR99	PEWCT1077	$1,971.47	$1,892.61	$1,813.75	$1,734.89	81
				30	20	CPR-90G	EAR99	PEWCT1081	$2,041.34	$1,959.69	$1,878.03	$1,796.38	82
				40	10	Square Cover UG-39/U	EAR99	PEWCT1070	$1,930.39	$1,853.17	$1,775.96	$1,698.74	83
				40	10	CPR-90G	EAR99	PEWCT1074	$2,000.27	$1,920.26	$1,840.25	$1,760.24	84
				40	10	Square Cover UG-39/U	EAR99	PEWCT1078	$2,079.02	$1,995.86	$1,912.70	$1,829.54	85
				40	10	CPR-90G	EAR99	PEWCT1082	$2,041.34	$1,959.69	$1,878.03	$1,796.38	86
				50	10	Square Cover UG-39/U	EAR99	PEWCT1071	$1,930.39	$1,853.17	$1,775.96	$1,698.74	87
				50	10	CPR-90G	EAR99	PEWCT1075	$2,000.27	$1,920.26	$1,840.25	$1,760.24	88
				50	10	Square Cover UG-39/U	EAR99	PEWCT1079	$2,079.02	$1,995.86	$1,912.70	$1,829.54	89
				50	10	CPR-90G	EAR99	PEWCT1083	$2,041.34	$1,959.69	$1,878.03	$1,796.38	90
WR-112	7.05 - 10			20	45	Square Cover UG-51/U	EAR99	PEWCT1084	$2,240.71	$2,151.08	$2,061.45	$1,971.82	91
				20	25	CPR-112G	EAR99	PEWCT1088	$2,142.16	$2,056.47	$1,970.79	$1,885.10	92
				20	45	Square Cover UG-51/U	EAR99	PEWCT1092	$2,139.73	$2,054.14	$1,968.55	$1,882.96	93
				20	25	CPR-112G	EAR99	PEWCT1096	$2,157.11	$2,070.83	$1,984.54	$1,898.26	94
				30	25	Square Cover UG-51/U	EAR99	PEWCT1085	$2,124.79	$2,039.80	$1,954.81	$1,869.82	95
				30	25	CPR-112G	EAR99	PEWCT1089	$2,142.16	$2,056.47	$1,970.79	$1,885.10	96
				30	25	Square Cover UG-51/U	EAR99	PEWCT1093	$2,139.73	$2,054.14	$1,968.55	$1,882.96	97
				30	25	CPR-112G	EAR99	PEWCT1097	$2,157.11	$2,070.83	$1,984.54	$1,898.26	98
				40	20	Square Cover UG-51/U	EAR99	PEWCT1086	$2,124.79	$2,039.80	$1,954.81	$1,869.82	99
				40	20	CPR-112G	EAR99	PEWCT1090	$2,142.16	$2,056.47	$1,970.79	$1,885.10	1
				40	20	Square Cover UG-51/U	EAR99	PEWCT1094	$2,139.73	$2,054.14	$1,968.55	$1,882.96	2
				40	20	CPR-112G	EAR99	PEWCT1098	$2,157.11	$2,070.83	$1,984.54	$1,898.26	3
				50	10	Square Cover UG-51/U	EAR99	PEWCT1087	$2,124.79	$2,039.80	$1,954.81	$1,869.82	4
				50	10	CPR-112G	EAR99	PEWCT1091	$2,142.16	$2,056.47	$1,970.79	$1,885.10	5
				50	10	Square Cover UG-51/U	EAR99	PEWCT1095	$2,139.73	$2,054.14	$1,968.55	$1,882.96	6
				50	10	CPR-112G	EAR99	PEWCT1099	$2,365.79	$2,271.16	$2,176.53	$2,081.90	7
WR-137	5.85 - 8.2			20	25	Round Cover UG-344/U	EAR99	PEWCT1100	$2,196.03	$2,108.19	$2,020.35	$1,932.51	8
				20	20	CPR-137G	EAR99	PEWCT1104	$2,157.09	$2,070.81	$1,984.52	$1,898.24	9
				20	25	Round Cover UG-344/U	EAR99	PEWCT1108	$2,199.78	$2,111.79	$2,023.80	$1,935.81	10

*These WG crossguide couplers are available as assemblies with termination and/or with WG to Coax Adapters, see WG Coupler Asemblies or visit our website

Crossguide* with Termination and WG to Coax Adapter

WG Type	RF Freq. (GHz.)	IL (dB)	Max VSWR	Coupling (dB)	Directivity (dB)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-137	5.85 - 8.2	0.1	1.05:1	20	20	CPR-137G	EAR99	PEWCT1112	$2,193.19	$2,105.46	$2,017.73	$1,930.01	11
				30	20	Round Cover UG-344/U	EAR99	PEWCT1101	$2,196.03	$2,108.19	$2,020.35	$1,932.51	12
				30	20	CPR-137G	EAR99	PEWCT1105	$2,189.38	$2,101.80	$2,014.23	$1,926.65	13
				30	20	Round Cover UG-344/U	EAR99	PEWCT1109	$2,199.78	$2,111.79	$2,023.80	$1,935.81	14
				30	20	CPR-137G	EAR99	PEWCT1113	$2,160.84	$2,074.41	$1,987.97	$1,901.54	15
				40	20	Round Cover UG-344/U	EAR99	PEWCT1102	$2,196.03	$2,108.19	$2,020.35	$1,932.51	16
				40	20	CPR-137G	EAR99	PEWCT1106	$2,157.09	$2,070.81	$1,984.52	$1,898.24	17
				40	20	Round Cover UG-344/U	EAR99	PEWCT1110	$2,319.79	$2,227.00	$2,134.21	$2,041.42	18
				40	20	CPR-137G	EAR99	PEWCT1114	$2,369.89	$2,275.09	$2,180.30	$2,085.50	19
				50	10	Round Cover UG-344/U	EAR99	PEWCT1103	$2,196.03	$2,108.19	$2,020.35	$1,932.51	20
				50	10	CPR-137G	EAR99	PEWCT1107	$2,189.38	$2,101.80	$2,014.23	$1,926.65	21
				50	10	Round Cover UG-344/U	EAR99	PEWCT1111	$2,199.78	$2,111.79	$2,023.80	$1,935.81	22
				50	10	CPR-137G	EAR99	PEWCT1115	$2,160.84	$2,074.41	$1,987.97	$1,901.54	23

WAVEGUIDE COUPLER ASSEMBLIES

WG Crossguide Coupler	WG Crossguide Coupler with Termination	WG Crossguide Coupler with Termination & Coax Adapter SMA/ Type N	Conn. Type
PEWCP1035	PEWCT1000	PEWCT1044	2.92mm
PEWCP1036	PEWCT1001	PEWCT1045	2.92mm
PEWCP1037	PEWCT1002	PEWCT1046	2.92mm
PEWCP1038	PEWCT1003	PEWCT1047	2.92mm
PEWCP1039	PEWCT1004	PEWCT1048	SMA
PEWCP1040	PEWCT1005	PEWCT1049	SMA
PEWCP1041	PEWCT1006	PEWCT1050	SMA
PEWCP1042	PEWCT1007	PEWCT1051	SMA
PEWCP1043	PEWCT1008	PEWCT1052	SMA
PEWCP1044	PEWCT1009	PEWCT1053	SMA
PEWCP1045	PEWCT1010	PEWCT1054	SMA
PEWCP1046	PEWCT1011	PEWCT1055	SMA
PEWCP1047	PEWCT1012	PEWCT1056	SMA
PEWCP1048	PEWCT1013	PEWCT1057	SMA
PEWCP1049	PEWCT1014	PEWCT1058	SMA
PEWCP1050	PEWCT1015	PEWCT1059	SMA
PEWCP1051	PEWCT1016	PEWCT1060	SMA
		PEWCT1064	N
PEWCP1052	PEWCT1017	PEWCT1061	SMA
		PEWCT1065	N
PEWCP1053	PEWCT1018	PEWCT1062	SMA
		PEWCT1066	N
PEWCP1054	PEWCT1019	PEWCT1063	SMA
		PEWCT1067	N
PEWCP1055	PEWCT1020	PEWCT1068	SMA
		PEWCT1076	N
PEWCP1056	PEWCT1021	PEWCT1069	SMA
		PEWCT1077	N
PEWCP1057	PEWCT1022	PEWCT1070	SMA
		PEWCT1078	N
PEWCP1058	PEWCT1023	PEWCT1071	SMA
		PEWCT1079	N
PEWCP1059	PEWCT1024	PEWCT1072	SMA
		PEWCT1080	N
PEWCP1060	PEWCT1025	PEWCT1073	SMA
		PEWCT1081	N

WG Crossguide Coupler	WG Crossguide Coupler with Termination	WG Crossguide Coupler with Termination & Coax Adapter SMA/ Type N	Conn. Type
PEWCP1061	PEWCT1026	PEWCT1074	SMA
		PEWCT1082	N
PEWCP1062	PEWCT1027	PEWCT1075	SMA
		PEWCT1083	N
PEWCP1063	PEWCT1028	PEWCT1084	SMA
		PEWCT1092	N
PEWCP1064	PEWCT1029	PEWCT1085	SMA
		PEWCT1093	N
PEWCP1065	PEWCT1030	PEWCT1086	SMA
		PEWCT1094	N
PEWCP1066	PEWCT1031	PEWCT1087	SMA
		PEWCT1095	N
PEWCP1067	PEWCT1032	PEWCT1088	SMA
		PEWCT1096	N
PEWCP1068	PEWCT1033	PEWCT1089	SMA
		PEWCT1097	N
PEWCP1069	PEWCT1034	PEWCT1090	SMA
		PEWCT1098	N
PEWCP1070	PEWCT1035	PEWCT1091	SMA
		PEWCT1099	N
PEWCP1071	PEWCT1036	PEWCT1100	SMA
		PEWCT1108	N
PEWCP1072	PEWCT1037	PEWCT1101	SMA
		PEWCT1109	N
PEWCP1073	PEWCT1038	PEWCT1102	SMA
		PEWCT1110	N
PEWCP1074	PEWCT1039	PEWCT1103	SMA
		PEWCT1111	N
PEWCP1075	PEWCT1040	PEWCT1104	SMA
		PEWCT1112	N
PEWCP1076	PEWCT1041	PEWCT1105	SMA
		PEWCT1113	N
PEWCP1077	PEWCT1042	PEWCT1106	SMA
		PEWCT1114	N
PEWCP1078	PEWCT1043	PEWCT1107	SMA
		PEWCT1115	N

*These WG crossguide couplers are available as assemblies with termination and/or with WG to Coax Adapters, see WG Coupler Asemblies or visit our website

WAVEGUIDE DETECTORS

Connector 1	RF Frequency (GHz.)	Voltage Sensitivity (V/nW)	Input Power (dBm)	Connector 2	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-28 UG-599/U	26.5 - 40	-1,000	20	SMA Female	EAR99	PE80T3005	$3,627.84	$3,482.73	$3,337.61	$3,192.50	24
WR-22 UG-383/U	33 - 50	-800		SMA Female	EAR99	PE80T3004	$4,377.60	$4,224.38	$4,071.17	$3,939.84	25
WR-19 UG-383/U	40 - 60	-800		SMA Female	EAR99	PE80T3003	$3,865.20	$3,710.59	$3,555.98	$3,401.38	26
WR-15 UG-385/U	50 - 75	-700		SMA Female	EAR99	PE80T3002	$4,628.16	$4,443.03	$4,257.91	$4,072.78	27
WR-12 UG-387/U	60 - 90	-900		SMA Female	EAR99	PE80T3001	$4,445.27	$4,267.46	$4,089.65	$3,911.84	28
WR-10 UG-387/U	75 - 100	-900		SMA Female	EAR99	PE80T3000	$4,288.89	$4,117.33	$3,945.78	$3,774.22	29

WAVEGUIDE DIRECT READ ATTENUATORS

WG Type	RF Freq. (GHz.)	Max Atten (dB)	IL (dB)	Max VSWR	Input Power (Watts)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-10	75 - 110	50	1	1.2:1	0.2	Round Cover UG-387/U-Mod	EAR99	PE-W10AT5001	$5,588.44	$5,364.90	$5,141.36	$4,917.83	30
WR-12	60 - 90		0.9	1.2:1	0.2	Round Cover UG-387/U	EAR99	PE-W12AT5001	$6,129.03	$5,914.51	$5,700.00	$5,516.13	31
WR-15	50 - 75		0.8	1.2:1	0.3	Round Cover UG-385/U	EAR99	PE-W15AT5001	$5,893.31	$5,657.58	$5,421.85	$5,186.11	32
WR-19	40 - 60		0.7	1.15:1	0.2	Round Cover UG-383/U-Mod	EAR99	PE-W19AT5001	$5,588.44	$5,364.90	$5,141.36	$4,917.83	33
WR-22	33 - 50		0.6	1.15:1	0.4	Round Cover UG-383/U	EAR99	PE-W22AT5001	$5,806.38	$5,574.12	$5,341.87	$5,109.61	34
		60		1.15:1	0.5		EAR99	PE-W22AT5002	$5,590.00	$5,366.40	$5,142.80	$4,919.20	35
WR-28	26.5 - 40	50	0.5	1.15:1	0.5	Square Cover UG-599/U	EAR99	PE-W28AT5001	$5,482.14	$5,262.85	$5,043.57	$4,824.28	36
WR-42	18 - 26.5			1.15:1	1	Square Cover UG-595/U	EAR99	PE-W42AT5001	$6,129.03	$5,883.87	$5,638.71	$5,393.55	37

WAVEGUIDE ELECTROMECHANICAL RELAY SWITCHES

Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
M: Manual Override
N: Normally Open
NT: Non-Terminated
P: Pulse Latching
R: Reflective
RS: Reset
S: Self Cut Off
SI: Set Indicator
T: Terminated
TTL: TTL Logic
V: Viewing Window

WG Type	Switch Type	RF Freq. (GHz.)	Actuator / Features	IL (dB)	Iso (dB)	DC Power (V)	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-28	SPDT/ DPDT	26.5 - 40	F, I	0.15	55	12	EAR99	PEWGS6056	Call	Call	Call	Call	38
				0.15	55	28	EAR99	PEWGS6057	Call	Call	Call	Call	39
			F, TTL, I	0.15	55	12	EAR99	PEWGS6058	Call	Call	Call	Call	40
				0.15	55	28	EAR99	PEWGS6059	Call	Call	Call	Call	41
	SPDT		B, L, S, I, M	0.15	55	12	EAR99	PEWGS6002	$3,714.09	$3,565.53	$3,416.96	$3,268.40	42
				0.15	55	28	EAR99	PEWGS6000	$3,684.68	$3,537.29	$3,389.91	$3,242.52	43
			B, L, TTL, S, I, M	0.15	55	12	EAR99	PEWGS6003	$4,204.68	$4,036.49	$3,868.31	$3,700.12	44
				0.15	55	28	EAR99	PEWGS6001	$3,828.39	$3,675.25	$3,522.12	$3,368.98	45
WR-34	SPDT/ DPDT	22 - 33	L, S, SI, M, V	0.15	60	12	EAR99	PEWGS6042	$4,489.34	$4,309.77	$4,130.19	$3,950.62	46
				0.15	60	28	EAR99	PEWGS6040	$4,556.55	$4,374.29	$4,192.03	$4,009.76	47
			L, TTL, S, SI, M, V	0.15	60	12	EAR99	PEWGS6043	$4,662.67	$4,476.16	$4,289.66	$4,103.15	48
				0.15	60	28	EAR99	PEWGS6041	$4,662.67	$4,476.16	$4,289.66	$4,103.15	49
WR-42	SPDT	18 - 26.5	B, L, S, I, M	0.15	60	12	EAR99	PEWGS6006	$3,714.09	$3,565.53	$3,416.96	$3,268.40	50
				0.15	60	28	EAR99	PEWGS6004	$3,630.33	$3,485.12	$3,339.90	$3,194.69	51
			B, L, TTL, S, I, M	0.15	60	12	EAR99	PEWGS6007	$3,714.09	$3,565.53	$3,416.96	$3,268.40	52
				0.15	60	28	EAR99	PEWGS6005	$3,828.39	$3,675.25	$3,522.12	$3,368.98	53
WR-62		12.4 - 18	B, L, S, I, M	0.1	60	12	EAR99	PEWGS6010	$3,521.96	$3,381.08	$3,240.20	$3,099.32	54
				0.1	60	28	EAR99	PEWGS6008	$3,630.33	$3,485.12	$3,339.90	$3,194.69	55
			B, L, TTL, S, I, M	0.1	60	12	EAR99	PEWGS6011	$3,957.14	$3,798.85	$3,640.57	$3,482.28	56
				0.1	60	28	EAR99	PEWGS6009	$4,296.02	$4,124.18	$3,952.34	$3,780.50	57
WR-75		10 - 15	B, L, S, I, M	0.05	75	12	EAR99	PEWGS6014	$3,521.96	$3,381.08	$3,240.20	$3,099.32	58
				0.05	75	28	EAR99	PEWGS6012	$3,828.39	$3,675.25	$3,522.12	$3,368.98	59
			B, L, TTL, S, I, M	0.05	75	12	EAR99	PEWGS6015	$3,521.96	$3,381.08	$3,240.20	$3,099.32	60
				0.05	75	28	EAR99	PEWGS6013	$4,109.70	$3,945.31	$3,780.92	$3,616.54	61
WR-90	SPDT/ DPDT	8.2 - 12.4	F, I	0.07	80	12	EAR99	PEWGS6060	Call	Call	Call	Call	62
				0.07	80		EAR99	PEWGS6064	Call	Call	Call	Call	63
				0.07	80	28	EAR99	PEWGS6061	Call	Call	Call	Call	64
				0.07	80		EAR99	PEWGS6065	Call	Call	Call	Call	65

WAVEGUIDE ELECTROMECHANICAL RELAY SWITCHES

Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
M: Manual Override
N: Normally Open
NT: Non-Terminated
P: Pulse Latching
R: Reflective
RS: Reset
S: Self Cut Off
SI: Set Indincator
T: Terminated
TTL: TTL Logic
V: Viewing Window

WG Type	Switch Type	RF Freq. (GHz.)	Actuator / Features	IL (dB)	Iso (dB)	DC Power (V)	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-90	SPDT/ DPDT	8.2 - 12.4	F, TTL, I	0.07	80	12	EAR99	PEWGS6062	Call	Call	Call	Call	66
				0.07	80		EAR99	PEWGS6066	Call	Call	Call	Call	67
				0.07	80	28	EAR99	PEWGS6063	Call	Call	Call	Call	68
				0.07	80		EAR99	PEWGS6067	Call	Call	Call	Call	69
	SPDT		B, L, S, I, M	0.07	80	12	EAR99	PEWGS6018	$4,438.58	$4,261.04	$4,083.49	$3,905.95	70
				0.07	80	28	EAR99	PEWGS6016	$4,142.67	$3,976.96	$3,811.26	$3,645.55	71
			B, L, TTL, S, I, M	0.07	80	12	EAR99	PEWGS6019	$4,390.32	$4,214.71	$4,039.09	$3,863.48	72
				0.07	80	28	EAR99	PEWGS6017	$3,828.39	$3,675.25	$3,522.12	$3,368.98	73
WR-102	SPDT/ DPDT	7 - 11	L, S, SI, M, V	0.06	80	12	EAR99	PEWGS6038	$4,489.34	$4,309.77	$4,130.19	$3,950.62	74
				0.06	80	28	EAR99	PEWGS6036	$4,489.34	$4,309.77	$4,130.19	$3,950.62	75
			L, TTL, S, SI, M, V	0.06	80	12	EAR99	PEWGS6039	$4,662.67	$4,476.16	$4,289.66	$4,103.15	76
				0.06	80	28	EAR99	PEWGS6037	$4,662.67	$4,476.16	$4,289.66	$4,103.15	77
WR-112		7.05 - 10	F, I	0.05	80	12	EAR99	PEWGS6068	Call	Call	Call	Call	78
				0.05	80	28	EAR99	PEWGS6069	Call	Call	Call	Call	79
			F, TTL, I	0.05	80	12	EAR99	PEWGS6070	Call	Call	Call	Call	80
				0.05	80		EAR99	PEWGS6071	Call	Call	Call	Call	81
	SPDT		B, L, S, I, M	0.05	80		EAR99	PEWGS6022	$3,521.96	$3,381.08	$3,240.20	$3,099.32	82
				0.05	80	28	EAR99	PEWGS6020	$3,630.33	$3,485.12	$3,339.90	$3,194.69	83
			B, L, TTL, S, I, M	0.05	80	12	EAR99	PEWGS6023	$3,714.09	$3,565.53	$3,416.96	$3,268.40	84
				0.05	80	28	EAR99	PEWGS6021	$3,630.33	$3,485.12	$3,339.90	$3,194.69	85
WR-137		5.85 - 8.2	B, L, S, I, M	0.02	70	12	EAR99	PEWGS6026	$3,521.96	$3,381.08	$3,240.20	$3,099.32	86
				0.02	70	28	EAR99	PEWGS6024	$3,828.39	$3,675.25	$3,522.12	$3,368.98	87
			B, L, TTL, S, I, M	0.02	70	12	EAR99	PEWGS6027	$3,521.96	$3,381.08	$3,240.20	$3,099.32	88
				0.02	70	28	EAR99	PEWGS6025	$3,630.33	$3,485.12	$3,339.90	$3,194.69	89
WR-159	SPDT/ DPDT	4.9 - 7.05	L, S, SI, M, V	0.06	70	12	EAR99	PEWGS6034	$4,489.34	$4,309.77	$4,130.19	$3,950.62	90
				0.06	70	28	EAR99	PEWGS6032	$4,489.34	$4,309.77	$4,130.19	$3,950.62	91
			L, TTL, S, SI, M, V	0.06	70	12	EAR99	PEWGS6033	$4,662.67	$4,476.16	$4,289.66	$4,103.15	92
				0.06	70		EAR99	PEWGS6035	$4,662.67	$4,476.16	$4,289.66	$4,103.15	93
WR-187		3.95 - 5.85	L, S, SI, M, V	0.02	80		EAR99	PEWGS6030	$4,489.34	$4,309.77	$4,130.19	$3,950.62	94
				0.02	80	28	EAR99	PEWGS6028	$4,489.03	$4,309.47	$4,129.91	$3,950.35	95
			L, TTL, S, SI, M, V	0.002	80	12	EAR99	PEWGS6031	$4,662.67	$4,476.16	$4,289.66	$4,103.15	96
				0.02	80	28	EAR99	PEWGS6029	$4,662.67	$4,476.16	$4,289.66	$4,103.15	97

DOUBLE RIDGE WAVEGUIDE ELECTROMECHANICAL RELAY SWITCHES

Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
M: Manual Override
N: Normally Open
NT: Non-Terminated
P: Pulse Latching
R: Reflective
RS: Reset
S: Self Cut Off
SI: Set Indincator
T: Terminated
TTL: TTL Logic
V: Viewing Window

WG Type	Switch Type	RF Freq. (GHz.)	Actuator / Features	IL (dB)	Iso (dB)	DC Power (V)	ECCN	Model No	1	2-4	5-9	10+	ROW
WRD-180	SPDT/ DPDT	18 - 40	L, S, SI, M, V	0.4	50	12	EAR99	PEWGS6054	$8,822.67	$8,469.76	$8,116.86	$7,763.95	98
				0.4	50	28	EAR99	PEWGS6052	$8,822.67	$8,469.76	$8,116.86	$7,763.95	99
			L, TTL, S, SI, M, V	0.4	50	12	EAR99	PEWG6056	Call	Call	Call	Call	1
				0.4	50		EAR99	PEWG6065	Call	Call	Call	Call	2
				0.4	50		EAR99	PEWG6066	Call	Call	Call	Call	3
				0.4	50		EAR99	PEWG6067	Call	Call	Call	Call	4
				0.4	50		EAR99	PEWG6068	Call	Call	Call	Call	5
				0.4	50		EAR99	PEWG6069	Call	Call	Call	Call	6
				0.4	50		EAR99	PEWG6070	Call	Call	Call	Call	7
				0.4	50		EAR99	PEWG6071	Call	Call	Call	Call	8
				0.4	50		EAR99	PEWG6057	Call	Call	Call	Call	9
				0.4	50		EAR99	PEWG6058	Call	Call	Call	Call	10
				0.4	50		EAR99	PEWG6059	Call	Call	Call	Call	11
				0.4	50		EAR99	PEWG6060	Call	Call	Call	Call	12
				0.4	50		EAR99	PEWG6061	Call	Call	Call	Call	13
				0.4	50		EAR99	PEWG6062	Call	Call	Call	Call	14
				0.4	50		EAR99	PEWGS6055	$8,996.00	$8,636.16	$8,276.32	$7,916.48	15
				0.4	50		EAR99	PEWG6063	Call	Call	Call	Call	16
				0.4	50		EAR99	PEWG6064	Call	Call	Call	Call	17
				0.4	50	28	EAR99	PEWGS6053	$8,996.00	$8,636.16	$8,276.32	$7,916.48	18

DOUBLE RIDGE WAVEGUIDE ELECTROMECHANICAL RELAY SWITCHES

Features:
A: Absorptive
AR: Auto Reset
F: Failsafe
D: Diode
GR: Global Reset
H: Hot Switches
I: Indicators
L: Latching
M: Manual Override
N: Normally Open
NT: Non-Terminated
P: Pulse Latching
R: Reflective
RS: Reset
S: Self Cut Off
SI: Set Indincator
T: Terminated
TTL: TTL Logic
V: Viewing Window

WG Type	Switch Type	RF Freq. (GHz.)	Actuator / Features	IL (dB)	Iso (dB)	DC Power (V)	ECCN	Model No	1	2-4	5-9	10+	ROW
WRD-650	SPDT/ DPDT	6.5 - 18	L, S, SI, M, V	0.35	60	12	EAR99	PEWGS6046	$7,956.00	$7,637.76	$7,319.52	$7,001.28	19
				0.35	60	28	EAR99	PEWGS6044	$8,075.11	$7,752.11	$7,429.10	$7,106.10	20
			L, TTL, S, SI, M, V	0.35	60	12	EAR99	PEWGS6047	$8,129.34	$7,804.17	$7,478.99	$7,153.82	21
				0.35	60	28	EAR99	PEWGS6045	$8,129.34	$7,804.17	$7,478.99	$7,153.82	22
WRD-750		7.5 - 18	L, S, SI, M, V	0.3	60	12	EAR99	PEWGS6050	$7,956.00	$7,637.76	$7,319.52	$7,001.28	23
				0.3	60	28	EAR99	PEWGS6048	$7,956.00	$7,637.76	$7,319.52	$7,001.28	24
			L, TTL, S, SI, M, V	0.3	60	12	EAR99	PEWGS6051	$8,129.34	$7,804.17	$7,478.99	$7,153.82	25
				0.3	60	28	EAR99	PEWGS6049	$8,129.34	$7,804.17	$7,478.99	$7,153.82	26

ELECTROMECHANICAL RELAY SWITCHES

see page 324

WAVEGUIDE FIXED ATTENUATORS

Waveguide Type	RF Frequency (GHz.)	Flange Type	Atten. (dB)	VSWR	Max. Power (W)	ECCN	Model No	1-24	25-49	50-99	100+	ROW
WR-10	75 - 110	Round Cover UG-387/U-Mod	3	1.15:1	1	EAR99	PEWAT1012-3	1,270.46	1,181.53	1,092.60	1,016.37	27
			6		1	EAR99	PEWAT1012-6	1,270.46	1,181.53	1,092.60	1,016.37	28
			10		1	EAR99	PEWAT1012-10	1,270.46	1,181.53	1,092.60	1,016.37	29
			20		1	EAR99	PEWAT1012-20	1,270.46	1,181.53	1,092.60	1,016.37	30
			30		1	EAR99	PEWAT1012-30	1,270.46	1,181.53	1,092.60	1,016.37	31
WR-12	60 - 90	Round Cover UG-387/U	3		1	EAR99	PEWAT1011-3	1,270.46	1,181.53	1,092.60	1,016.37	32
			6		1	EAR99	PEWAT1011-6	1,270.46	1,181.53	1,092.60	1,016.37	33
			10		1	EAR99	PEWAT1011-10	1,270.46	1,181.53	1,092.60	1,016.37	34
			20		1	EAR99	PEWAT1011-20	1,270.46	1,181.53	1,092.60	1,016.37	35
			30		1	EAR99	PEWAT1011-30	1,270.46	1,181.53	1,092.60	1,016.37	36
WR-15	50 - 75	Round Cover UG-385/U	3		2	EAR99	PEWAT1010-3	1,270.46	1,181.53	1,092.60	1,016.37	37
			6		2	EAR99	PEWAT1010-6	1,270.46	1,181.53	1,092.60	1,016.37	38
			10		2	EAR99	PEWAT1010-10	1,270.46	1,181.53	1,092.60	1,016.37	39
			20		2	EAR99	PEWAT1010-20	1,270.46	1,181.53	1,092.60	1,016.37	40
			30		2	EAR99	PEWAT1010-30	1,270.46	1,181.53	1,092.60	1,016.37	41
WR-19	40 - 60	Round Cover UG-383/U-Mod	3		3	EAR99	PEWAT1009-3	1,465.91	1,363.30	1,260.68	1,172.73	42
			6		3	EAR99	PEWAT1009-6	1,465.91	1,363.30	1,260.68	1,172.73	43
			10		3	EAR99	PEWAT1009-10	1,465.91	1,363.30	1,260.68	1,172.73	44
			20		3	EAR99	PEWAT1009-20	1,465.91	1,363.30	1,260.68	1,172.73	45
			30		3	EAR99	PEWAT1009-30	1,465.91	1,363.30	1,260.68	1,172.73	46
WR-22	33 - 50	Round Cover UG-383/U	3		4	EAR99	PEWAT1008-3	1,465.91	1,363.30	1,260.68	1,172.73	47
			6		4	EAR99	PEWAT1008-6	1,465.91	1,363.30	1,260.68	1,172.73	48
			10		4	EAR99	PEWAT1008-10	1,465.91	1,363.30	1,260.68	1,172.73	49
			20		4	EAR99	PEWAT1008-20	1,465.91	1,363.30	1,260.68	1,172.73	50
			30		4	EAR99	PEWAT1008-30	1,465.91	1,363.30	1,260.68	1,172.73	51
WR-28	26.5 - 40	Square Cover UG-599/U	3		5	EAR99	PEWAT1007-3	1,465.91	1,363.30	1,260.68	1,172.73	52
			6		5	EAR99	PEWAT1007-6	1,465.91	1,363.30	1,260.68	1,172.73	53
			10	1.2:1	5	EAR99	PEWAT1007-10	1,465.91	1,363.30	1,260.68	1,172.73	54
			20		5	EAR99	PEWAT1007-20	1,465.91	1,363.30	1,260.68	1,172.73	55
			30	1.15:1	5	EAR99	PEWAT1007-30	1,465.91	1,363.30	1,260.68	1,172.73	56

FLEXIBLE WAVEGUIDES

Seamless

Waveguide Type	RF Frequency (GHz.)	IL (dB)	Max VSWR	Length (in)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-22	33 - 50	0.49	1.2:1	6	Round Cover UG-383/U	EAR99	PE-W22SF005-6	$1,712.81	$1,644.30	$1,575.79	$1,507.27	57
		0.49	1.2:1	12	Round Cover UG-383/U	EAR99	PE-W22SF005-12	$2,568.67	$2,465.92	$2,363.18	$2,260.43	58
		0.49	1.2:1	24	Round Cover UG-383/U	EAR99	PE-W22SF005-24	$3,464.07	$3,325.51	$3,186.94	$3,048.38	59
WR-28	26.5 - 40	0.49	1.2:1	12	Square Cover UG-599/U	EAR99	PE-W28SF005-12	$1,451.75	$1,393.68	$1,335.61	$1,277.54	60
		0.98	1.2:1	24	Square Cover UG-599/U	EAR99	PE-W28SF005-24	$2,308.90	$2,216.54	$2,124.19	$2,031.83	61
		1.47	1.2:1	36	Square Cover UG-599/U	EAR99	PE-W28SF005-36	$3,221.91	$3,093.03	$2,964.16	$2,835.28	62
WR-34	22 - 33	0.4	1.15:1	12	Square Cover UG-1530/U	EAR99	PE-W34SF005-12	$1,395.90	$1,340.06	$1,284.23	$1,228.39	63
		0.8	1.15:1	24	Square Cover UG-1530/U	EAR99	PE-W34SF005-24	$2,189.46	$2,101.88	$2,014.30	$1,926.72	64
		1.2	1.15:1	36	Square Cover UG-1530/U	EAR99	PE-W34SF005-36	$3,221.91	$3,093.03	$2,964.16	$2,835.28	65
WR-42	18 - 26.5	0.27	1.15:1	12	Square Cover UG-595/U	EAR99	PE-W42SF005-12	$1,226.13	$1,177.08	$1,128.04	$1,078.99	66
		0.54	1.15:1	24	Square Cover UG-595/U	EAR99	PE-W42SF005-24	$1,991.99	$1,912.31	$1,832.63	$1,752.95	67
		0.81	1.15:1	36	Square Cover UG-595/U	EAR99	PE-W42SF005-36	$2,761.63	$2,651.16	$2,540.70	$2,430.23	68
WR-51	15 - 22	0.18	1.1:1	12	Square Cover	EAR99	PE-W51SF005-12	$1,173.43	$1,126.49	$1,079.56	$1,032.62	69
		0.36	1.1:1	24	Square Cover	EAR99	PE-W51SF005-24	$1,896.11	$1,820.27	$1,744.42	$1,668.58	70
		0.54	1.1:1	36	Square Cover	EAR99	PE-W51SF005-36	$2,665.24	$2,558.63	$2,452.02	$2,345.41	71
WR-62	12.4 - 18	0.14	1.08:1	12	Square Cover UG-419/U	EAR99	PE-W62SF005-12	$1,177.09	$1,130.01	$1,082.92	$1,035.84	72
		0.28	1.08:1	24	Square Cover UG-419/U	EAR99	PE-W62SF005-24	$1,699.36	$1,631.39	$1,563.41	$1,495.44	73
		0.42	1.08:1	36	Square Cover UG-419/U	EAR99	PE-W62SF005-36	$2,418.93	$2,322.17	$2,225.42	$2,128.66	74
WR-75	10 - 15	0.12	1.07:1	12	Square Cover	EAR99	PE-W75SF005-12	$1,150.70	$1,104.67	$1,058.64	$1,012.62	75
		0.24	1.07:1	24	Square Cover	EAR99	PE-W75SF005-24	$1,859.80	$1,785.41	$1,711.02	$1,636.62	76
		0.36	1.07:1	36	Square Cover	EAR99	PE-W75SF005-36	$2,526.83	$2,425.76	$2,324.68	$2,223.61	77
WR-90	8.2 - 12.4	0.09	1.07:1	12	Square Cover UG-39/U	EAR99	PE-W90SF005-12	$1,224.17	$1,175.20	$1,126.24	$1,077.27	78
		0.18	1.07:1	24	CPR-90G	EAR99	PE-W90SF006-24	$1,745.85	$1,676.02	$1,606.18	$1,536.35	79
		0.18	1.07:1		Square Cover UG-39/U	EAR99	PE-W90SF005-24	$1,841.11	$1,767.47	$1,693.82	$1,620.18	80
		0.27	1.07:1	36	CPR-90G	EAR99	PE-W90SF006-36	$2,368.35	$2,273.62	$2,178.88	$2,084.15	81
		0.27	1.07:1		Square Cover UG-39/U	EAR99	PE-W90SF005-36	$2,497.56	$2,397.66	$2,297.76	$2,197.85	82
		0.9	1.07:1	12	CPR-90G	EAR99	PE-W90SF006-12	$1,116.20	$1,071.55	$1,026.90	$982.26	83
WR-112	7.05 - 10	0.08	1.07:1		CPR-112G	EAR99	PE-W112SF006-12	$1,209.22	$1,160.85	$1,112.48	$1,064.11	84
		0.08	1.07:1		Square Cover UG-51/U	EAR99	PE-W112SF005-12	$1,227.33	$1,178.24	$1,129.14	$1,080.05	85
		0.16	1.07:1	24	CPR-112G	EAR99	PE-W112SF006-24	$1,903.25	$1,827.12	$1,750.99	$1,674.86	86
		0.16	1.07:1		Square Cover UG-51/U	EAR99	PE-W112SF005-24	$1,931.74	$1,854.47	$1,777.20	$1,699.93	87
		0.24	1.07:1	36	CPR-112G	EAR99	PE-W112SF006-36	$2,604.46	$2,500.28	$2,396.10	$2,291.92	88
		0.24	1.07:1		Square Cover UG-51/U	EAR99	PE-W112SF005-36	$2,604.46	$2,500.28	$2,396.10	$2,291.92	89
WR-137	5.85 - 8.2	0.06	1.07:1	12	CPR-137G	EAR99	PE-W137SF006-12	$1,237.83	$1,188.32	$1,138.80	$1,089.29	90
		0.06	1.07:1		Round Cover UG-344/U	EAR99	PE-W137SF005-12	$1,345.15	$1,291.34	$1,237.54	$1,183.73	91
		0.12	1.07:1	24	CPR-137G	EAR99	PE-W137SF006-24	$2,124.19	$2,039.22	$1,954.25	$1,869.29	92
		0.12	1.07:1		Round Cover UG-344/U	EAR99	PE-W137SF005-24	$2,139.37	$2,053.80	$1,968.22	$1,882.65	93
		0.18	1.07:1	36	CPR-137G	EAR99	PE-W137SF006-36	$2,883.51	$2,768.17	$2,652.83	$2,537.49	94
		0.18	1.07:1		Round Cover UG-344/U	EAR99	PE-W137SF005-36	$2,933.58	$2,816.24	$2,698.89	$2,581.55	95

Twistable

Waveguide Type	RF Frequency (GHz.)	IL (dB)	Max VSWR	Length (in)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
WR-22	33 - 50	0.6	1.3:1	6	Round Cover UG-383/U	EAR99	PE-W22TF005-6	$860.18				96
		0.6	1.3:1	12	Round Cover UG-383/U	EAR99	PE-W22TF005-12	$875.28				97
		0.6	1.3:1	24	Round Cover UG-383/U	EAR99	PE-W22TF005-24	$920.55				98
WR-28	26.5 - 40	0.6	1.3:1	12	Square Cover UG-599/U	EAR99	PE-W28TF005-12	$566.78				99
		1.2	1.3:1	24	Square Cover UG-599/U	EAR99	PE-W28TF005-24	$635.41				1
		1.8	1.3:1	36	Square Cover UG-599/U	EAR99	PE-W28TF005-36	$620.28				2
WR-34	22 - 33	0.5	1.22:1	12	Square Cover UG-1530/U	EAR99	PE-W34TF005-12	$526.90				3
		1	1.22:1	24	Square Cover UG-1530/U	EAR99	PE-W34TF005-24	$593.24				4
		1.5	1.22:1	36	Square Cover UG-1530/U	EAR99	PE-W34TF005-36	$635.02				5
WR-42	18 - 26.5	0.35	1.3:1	12	Square Cover UG-595/U	EAR99	PE-W42TF005-12	$487.71				6
		0.7	1.3:1	24	Square Cover UG-595/U	EAR99	PE-W42TF005-24	$518.04				7
		1.05	1.35:1	36	Square Cover UG-595/U	EAR99	PE-W42TF005-36	$542.02				8
WR-51	15 - 22	0.55	1.15:1	12	Square Cover	EAR99	PE-W51TF005-12	$515.19				9

Twistable

Waveguide Type	RF Frequency (GHz.)	IL (dB)	Max VSWR	Length (in)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
WR-51	15 - 22	1.1	1.15:1	24	Square Cover	EAR99	PE-W51TF005-24	$535.74		See Web for Volume Pricing		10
		1.65	1.15:1	36	Square Cover	EAR99	PE-W51TF005-36	$596.32				11
WR-62	12.4 - 18	0.28	1.1:1	12	Square Cover UG-419/U	EAR99	PE-W62TF005-12	$574.60				12
		0.56	1.1:1	24	Square Cover UG-419/U	EAR99	PE-W62TF005-24	$668.47				13
		0.84	1.1:1	36	Square Cover UG-419/U	EAR99	PE-W62TF005-36	$683.22				14
WR-75	10 - 15	0.18	1.1:1	12	Square Cover	EAR99	PE-W75TF005-12	$629.75				15
		0.36	1.1:1	24	Square Cover	EAR99	PE-W75TF005-24	$626.67				16
		0.54	1.1:1	36	Square Cover	EAR99	PE-W75TF005-36	$674.31				17
WR-90	8.2 - 12.4	0.15	1.07:1	12	CPR-90G	EAR99	PE-W90TF006-12	$535.74				18
		0.15	1.1:1		Square Cover UG-39/U	EAR99	PE-W90TF005-12	$680.95				19
		0.3	1.07:1	24	CPR-90G	EAR99	PE-W90TF006-24	$650.64				20
		0.36	1.1:1		Square Cover UG-39/U	EAR99	PE-W90TF005-24	$726.67				21
		0.45	1.07:1	36	CPR-90G	EAR99	PE-W90TF006-36	$714.12				22
		0.45	1.1:1		Square Cover UG-39/U	EAR99	PE-W90TF005-36	$742.69				23
WR-112	7.05 - 10	0.12	1.07:1	12	CPR-112G	EAR99	PE-W112TF006-12	$676.80				24
		0.12	1.3:1		Square Cover UG-51/U	EAR99	PE-W112TF005-12	$699.07				25
		0.24	1.07:1	24	CPR-112G	EAR99	PE-W112TF006-24	$759.00				26
		0.24	1.07:1		Square Cover UG-51/U	EAR99	PE-W112TF005-24	$714.11				27
		0.36	1.07:1	36	CPR-112G	EAR99	PE-W112TF006-36	$792.58				28
		0.36	1.07:1		Square Cover UG-51/U	EAR99	PE-W112TF005-36	$792.58				29
WR-137	5.85 - 8.2	0.07	1.05:1	12	CPR-137G	EAR99	PE-W137TF006-12	$650.64				30
		0.07	1.05:1		Round Cover UG-344/U	EAR99	PE-W137TF005-12	$651.13				31
		0.14	1.05:1	24	CPR-137G	EAR99	PE-W137TF006-24	$742.69				32
		0.14	1.05:1		Round Cover UG-344/U	EAR99	PE-W137TF005-24	$813.56				33
		0.18	1.05:1	36	Round Cover UG-344/U	EAR99	PE-W137TF005-36	$918.15				34
		0.21	1.05:1		CPR-137G	EAR99	PE-W137TF006-36	$846.15				35

WAVEGUIDE GUNN OSCILLATORS



WG Type	Center Freq. (GHz.)	Tuning Range (GHz.)	Integrated Heatsink	Phase Noise (dBc/Hz)	Output Power (dBm)	Flange Type	ECCN	Model No	1-9	10-24	25-49	50+	ROW
WR-42	24.125	+/- 1	No	-98	12.5	Square Cover UG-595/U	EAR99	PEWGN1012	$1,356.18	$1,288.37	$1,220.56	$1,166.31	36
WR-28	35	+/- 3	No	-95	15	Square Cover UG-599/U	EAR99	PEWGN1010	$8,051.18	$7,648.62	$7,246.06	$6,924.01	37
		+/- 3	Yes	-95	15	Square Cover UG-599/U	EAR99	PEWGN1011	$7,639.18	$7,257.22	$6,875.26	$6,569.69	38
WR-90	93.75	+/- 0.25	No	-105	18.5	Square Cover UG-39/U	EAR99	PEWGN1013	$3,828.18	$3,636.77	$3,445.36	$3,292.23	39

WAVEGUIDE ISOLATORS

WG Type	RF Freq. (GHz.)	Min Isolation (dB)	Max IL (dB)	Max VSWR	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-10	75 - 110	25	2.3	1.5:1	UG-387/U-Mod		PEWIR1000	Call	Call	Call	Call	40
WR-12	60 - 90		2	1.5:1	UG-387/U		PEWIR1001	$2,821.60	$2,708.74	$2,595.87	$2,483.01	41
WR-15	50 - 75		1.8	1.4:1	UG-385/U		PEWIR1002	$2,717.05	$2,608.37	$2,499.69	$2,391.00	42
WR-19	40 - 60		1.6	1.4:1	UG-383/U-Mod		PEWIR1003	$2,821.60	$2,708.74	$2,595.87	$2,483.01	43
WR-22	33 - 50		1.5	1.4:1	UG-383/U		PEWIR1004	$2,772.27	$2,661.38	$2,550.49	$2,439.60	44
WR-28	26.5 - 40				UG-599/U		PEWIR1015	$2,985.97	$2,866.53	$2,747.09	$2,627.65	45
WR-42	18 - 26.5				UG-597/U		PEWIR1010	$2,487.83	$2,388.32	$2,288.80	$2,189.29	46
WR-62	12.4 - 18				UG-1665/U		PEWIR1009	$2,412.86	$2,316.35	$2,219.83	$2,123.32	47
WR-75	10 - 15				Cover		PEWIR1008	$2,327.91	$2,234.79	$2,141.68	$2,048.56	48
WR-90	8.2 - 12.4				UG-135/U		PEWIR1007	$2,371.18	$2,276.33	$2,181.49	$2,086.64	49
WR-112	7.05 - 10				UG-138/U		PEWIR1006	$2,466.50	$2,367.84	$2,269.18	$2,170.52	50

WAVEGUIDE LOW NOISE AMPLIFIERS

RF Freq. (GHz.)	Gain (dB)	Gain Variation ± (dB)	NF (dB)	P1dB (dBm)	IP3 (dBm)	Waveguide Type	ECCN	Model No	1	2-4	5-9	10+	ROW
26.5 - 40	47	2.5	3.2	20	25	WR-28	EAR99	PE15A1076	$9,871.27	$9,476.42	$9,081.57	$8,686.72	51
27 - 40	35	3	3	10	20		EAR99	PE15A1077	$9,114.65	$8,750.06	$8,385.48	$8,020.89	52

WAVEGUIDE MAGIC TEES

Waveguide Type	RF Frequency (GHz.)	Flange Type	IL (dB)	Min Isolation (dB)	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-10	75 - 110	Round Cover UG-387/U-Mod	1	25	EAR99	PEWMT1000	$2,786.39	$2,674.93	$2,563.48	$2,452.02	53
WR-12	60 - 90	Round Cover UG-387/U			EAR99	PEWMT1001	$2,815.03	$2,702.43	$2,589.83	$2,477.23	54
WR-15	50 - 75	Round Cover UG-385/U			EAR99	PEWMT1002	$2,670.14	$2,563.33	$2,456.53	$2,349.72	55
WR-19	40 - 60	Round Cover UG-383/U-Mod	0.8		EAR99	PEWMT1003	$2,408.23	$2,311.90	$2,215.57	$2,119.24	56
WR-22	33 - 50	Round Cover UG-383/U	0.7		EAR99	PEWMT1004	$2,408.23	$2,311.90	$2,215.57	$2,119.24	57
WR-28	26.5 - 40	Square Cover UG-599/U	0.5		EAR99	PEWMT1005	$2,293.98	$2,202.22	$2,110.46	$2,018.70	58
WR-42	18 - 26.5	Square Cover UG-595/U			EAR99	PEWMT1006	$2,249.01	$2,159.05	$2,069.09	$1,979.13	59

WAVEGUIDE ORTHOMODE TRANSDUCERS



RF Freq. (GHz.)	H to A IL (dB)	V to A IL (dB)	H to V Isolation (dB)	H to A Cross Polariza-tion (dB)	V to A Cross Polariza-tion (dB)	Waveguide Type	ECCN	Model No	1	2-4	5-9	10+	ROW
24 - 33	0.6	0.5	45	35	35	WR-34	EAR99	PEWOT0001	$5,371.65	$5,183.64	$4,995.63	$4,834.49	60
30 - 42	0.5		40	35	35	WR-28	EAR99	PEWOT0003	$5,096.18	$4,917.81	$4,739.45	$4,586.56	61
26.5 - 40				35	35		EAR99	PEWOT0007	$4,820.71	$4,651.99	$4,483.26	$4,338.64	62
60 - 90	1.2	0.8		35	35	WR-12	EAR99	PEWOT0009	$4,848.25	$4,678.56	$4,508.87	$4,363.43	63
8.2 - 12.4						WR-90	EAR99	PEWOT0014	$3,856.57	$3,721.59	$3,586.61	$3,470.91	64

WAVEGUIDE PHASE SHIFTERS

WG Type	RF Freq. (GHz.)	Phase Range (GHz.)	Input Power (Watts)	IL (dB)	Length (in)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-10	75 - 110	0 - 180°	0.6	1	3	Round Cover UG-387/U-Mod	EAR99	PE-W10PS1001	$2,207.30	$2,119.01	$2,030.72	$1,942.42	65
WR-12	60 - 90	0 - 180°	0.7	1	3	Round Cover UG-387/U	EAR99	PE-W12PS1001	$2,293.38	$2,201.64	$2,109.91	$2,018.17	66
WR-15	50 - 75	0 - 180°	0.8	1	3	Round Cover UG-385/U	EAR99	PE-W15PS1001	$2,259.55	$2,169.17	$2,078.79	$1,988.40	67
WR-19	40 - 60	0 - 180°	1	1	3	Round Cover UG-383/U-Mod	EAR99	PE-W19PS1001	$2,174.74	$2,087.75	$2,000.76	$1,913.77	68
WR-22	33 - 50	0 - 180°	1	1	4	Round Cover UG-383/U	EAR99	PE-W22PS1001	$2,293.38	$2,201.64	$2,109.91	$2,018.17	69
WR-28	26.5 - 40	0 - 180°	1		4	Square Cover UG-599/U	EAR99	PE-W28PS1002	$2,848.99	$2,735.03	$2,621.07	$2,507.11	70
WR-42	18 - 26.5	0 - 180°	1.5	1	4	Square Cover UG-595/U	EAR99	PE-W42PS1001	$2,293.38	$2,201.64	$2,109.91	$2,018.17	71

WAVEGUIDE PIN DIODE SWITCHES

WG Type	Switch Type	RF Freq. (GHz.)	IL (dB)	Min Isolation (dB)	Max Switching (in)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-10	SPST/ Reflective	75 - 110	5.5	20	300	Round Cover UG-387/U	EAR99	PE71S9003	$8,669.44	$8,322.66	$7,975.88	$7,629.11	72
	SPDT/ Reflective		7	20	300	Round Cover UG-387/U	EAR99	PE71S9004	$10,294.96	$9,883.16	$9,471.36	$9,059.56	73
WR-12	SPST/ Reflective	60 - 90	4.5	20	300	Round Cover UG-387/U	EAR99	PE71S9001	$7,946.63	$7,628.76	$7,310.90	$6,993.03	74
	SPDT/ Reflective		6	20	300	Round Cover UG-387/U	EAR99	PE71S9002	$9,392.27	$9,016.58	$8,640.89	$8,265.20	75

PIN DIODE SWITCHES, see page 331

WAVEGUIDE POLARIZERS

Band	RF Freq. (GHz.)	Typ Band-width (GHz)	Typ IL (dB)	Typ Axial Ratio (dB)	Length (in)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
Ku	14 - 16	±1	0.5	1.1	3	Square Cover-UG-419/U-Mod	EAR99	PEWPL0000	$4,223.00	$4,075.20	$3,927.39	$3,800.70	76
Ka	26 - 33	±3.5		1.1	2	Square Cover-UG-599/U-Mod	EAR99	PEWPL0005	$4,223.00	$4,075.20	$3,927.39	$3,800.70	77
V	58 - 63	±2.5		1.1	1	Round Cover-UG-385/U-Mod	EAR99	PEWPL0008	$4,223.00	$4,075.20	$3,927.39	$3,800.70	78

WAVEGUIDE POWER AMPLIFIERS

Waveguide Type	RF Frequency (GHz.)	Min Gain (dB)	Psat (dBm)	Flange Type	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-12	70.5 - 76.5	25	20	Round Cover UG-387/U	EAR99	PE15A4023	$11,090.00	$10,646.40	$10,202.80	$9,759.20	79
	80.5 - 86.5	20	19	Round Cover UG-387/U	EAR99	PE15A4024	$11,537.55	$11,076.05	$10,614.55	$10,153.04	80

WAVEGUIDE SECTIONS

WG Type	RF Freq. (GHz.)	IL (dB)	VSWR	Length (in)	Flange Type	ECCN	Model No	1-9	10-24	25-49	50+	ROW
WR-5	140 - 220		1.15:1	1	Round Cover UG-387/U-Mod	EAR99	PEW05S000-1	$620.84	$589.80	$558.76	$533.92	81
				3		EAR99	PEW05S000-3	$577.19	$548.33	$519.47	$496.38	82
				6		EAR99	PEW05S000-6	$740.86	$703.82	$666.77	$637.14	83
				9		EAR99	PEW05S000-9	$837.43	$795.56	$753.69	$720.19	84
				12		EAR99	PEW05S000-12	$980.90	$931.86	$882.81	$843.57	85
WR-6	110 - 170	0.35		1		EAR99	PEW06S000-1	$500.83	$475.79	$450.75	$430.71	86
				3		EAR99	PEW06S000-3	$544.46	$517.24	$490.01	$468.24	87
		0.55		6		EAR99	PEW06S000-6	$697.68	$662.80	$627.91	$600.00	88
		0.75		9		EAR99	PEW06S000-9	$805.18	$764.92	$724.66	$692.45	89
		1.5		12		EAR99	PEW06S000-12	$934.18	$887.47	$840.76	$803.39	90
WR-8	90 - 140	0.3		1		EAR99	PEW08S000-1	$435.36	$413.59	$391.82	$374.41	91
				3		EAR99	PEW08S000-3	$479.00	$455.05	$431.10	$411.94	92
		0.5		6		EAR99	PEW08S000-6	$653.57	$620.89	$588.21	$562.07	93

WAVEGUIDE SECTIONS

WG Type	RF Freq. (GHz.)	IL (dB)	VSWR	Length (in)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-8	90 - 140	0.7	1.15:1	9	Round Cover UG-387/U-Mod	EAR99	PEW08S000-9	$805.18	See Web for Volume Pricing	94
		1.2		12		EAR99	PEW08S000-12	$948.17		95
WR-10	75 - 110	0.25	1.06:1	3		EAR99	PEW10S010-3	$503.41		96
		0.5		6		EAR99	PEW10S010-6	$515.41		97
WR-12	60 - 90	0.3		3	Round Cover UG-387/U	EAR99	PEW12S010-3	$391.73		98
		0.5		6		EAR99	PEW12S010-6	$412.47		99
		0.64		9		EAR99	PE-W12S001-9	$513.24		1
		0.8				EAR99	PEW12S010-9	$513.24		2
		0.82		12		EAR99	PE-W12S001-12	$532.95		3
WR-15	50 - 75	0.2		3	Round Cover UG-385/U	EAR99	PE-W15S001-3	$418.71		4
		0.34		6		EAR99	PE-W15S001-6	$426.23		5
		0.49		9		EAR99	PE-W15S001-9	$501.83		6
		0.64		12		EAR99	PE-W15S001-12	$699.32		7
		0.95				EAR99	PEW15S010-12	$699.32		8
WR-19	40 - 60	0.15		3	Round Cover UG-383/U-Mod	EAR99	PE-W19S001-3	$388.78		9
		0.2				EAR99	PEW19S010-3	$388.78		10
		0.25		6		EAR99	PE-W19S001-6	$441.01		11
		0.34		9		EAR99	PE-W19S001-9	$501.83		12
		0.44		12		EAR99	PE-W19S001-12	$570.26		13
		0.8				EAR99	PEW19S010-12	$561.84		14
WR-22	33 - 50	0.13		3	Round Cover UG-383/U	EAR99	PE-W22S001-3	$385.10		15
		0.21		6		EAR99	PE-W22S001-6	$405.04		16
		0.25	1.1:1	3		EAR99	PEW22S010-3	$428.93		17
		0.29	1.06:1	9		EAR99	PE-W22S001-9	$458.34		18
		0.36		12		EAR99	PE-W22S001-12	$551.25		19
			1.09:1	4		EAR99	PEWSP1000	$634.77		20
WR-28	26.5 - 40	0.11	1.06:1	3	Square Cover UG-599/U	EAR99	PE-W28S001-3	$363.03		21
		0.2				EAR99	PEW28S010-3	$396.08		22
				6		EAR99	PEW28S010-6	$441.91		23
		0.22		9		EAR99	PE-W28S001-9	$475.22		24
			1.09:1	4		EAR99	PEWSP1001	$560.08		25
WR-34	20 - 33		1.07:1		Square Cover UG-1530/U	EAR99	PEWSP1002	$578.76		26
WR-42	18 - 26.5	0.08	1.06:1	3	Square Cover UG-595/U	EAR99	PE-W42S002-3	$428.93		27
		0.12		6		EAR99	PE-W42S001A-6	$398.69		28
		0.15		9		EAR99	PE-W42S001A-9	$470.32		29
		0.18		12		EAR99	PE-W42S001-12	$572.74		30
			1.07:1	4		EAR99	PEWSP1003	$560.08		31
WR-51	15 - 22	0.11	1.06:1	9	UBR180	EAR99	PE-W51S001-9	$399.92		32
		0.13		12		EAR99	PE-W51S001-12	$541.16		33
			1.07:1	4	Square Cover	EAR99	PEWSP1004	$597.44		34
WR-62	12.4 - 18	0.08	1.06:1	6	Square Cover UG-419/U	EAR99	PE-W62S002-6	$456.89		35
		0.1		9		EAR99	PE-W62S002-9	$542.16		36
		0.11		12		EAR99	PE-W62S002-12	$613.85		37
			1.03:1	3		EAR99	PE-W62S001-3	$341.08		38
			1.07:1	4		EAR99	PEWSP1005	$576.07		39
			1.03:1	6		EAR99	PE-W62S001-6	$348.44		40
				9		EAR99	PE-W62S001-9	$355.78		41
				12		EAR99	PE-W62S001-12	$363.11		42
WR-75	10 - 15	0.1		6	UBR120	EAR99	PE-W75S001A-6	$336.05		43
				3		EAR99	PE-W75S001-3	$350.72		44
			1.07:1	4	Square Cover	EAR99	PEWSP1006	$587.43		45
			1.03:1	6	UBR120	EAR99	PE-W75S001-6	$341.08		46
				9		EAR99	PE-W75S001-9	$348.44		47
WR-90	8.2 - 12.4	0.1			Square Cover UG-39/U	EAR99	PE-W90S001A-9	$256.56		48
				3		EAR99	PE-W90S001-3	$223.73		49
					CPR-90G	EAR99	PE-W90S002-3	$276.87		50
			1.07:1	4	Square Cover UG-39/U	EAR99	PEWSP1007	$606.38		51
					CPR-90G	EAR99	PEWSP1008	$604.89		52
			1.03:1	6	Square Cover UG-39/U	EAR99	PE-W90S001-6	$227.39		53
					CPR-90G	EAR99	PE-W90S002-6	$325.88		54
				9	Square Cover UG-39/U	EAR99	PE-W90S001-9	$260.41		55
					CPR-90G	EAR99	PE-W90S002-9	$324.84		56
				12	Square Cover UG-39/U	EAR99	PE-W90S001-12	$272.26		57
					CPR-90G	EAR99	PE-W90S002-12	$337.83		58

WAVEGUIDE SECTIONS

WG Type	RF Freq. (GHz.)	IL (dB)	VSWR	Length (in)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
WR-112	7.05 - 10		1.03:1	3	Square Cover UG-51/U	EAR99	PE-W112S001-3	$344.76		See Web for Volume Pricing		59
			1.07:1	4		EAR99	PEWSP1009	$616.09				60
					CPR-112G	EAR99	PEWSP1010	$619.84				61
			1.03:1	6	Square Cover UG-51/U	EAR99	PE-W112S001-6	$331.35				62
				9		EAR99	PE-W112S001-9	$379.42				63
				12		EAR99	PE-W112S001-12	$350.83				64
WR-137	5.85 - 8.2	0.1		6	CPR-137G	EAR99	PE-W137S002A-6	$390.26				65
				3	Round Cover UG-344/U	EAR99	PE-W137S001-3	$367.90				66
					CPR-137G	EAR99	PE-W137S002-3	$366.77				67
			1.07:1	4	Round Cover UG-344/U	EAR99	PEWSP1011	$642.24				68
					CPR-137G	EAR99	PEWSP1012	$636.68				69
			1.03:1	6	Round Cover UG-344/U	EAR99	PE-W137S001-6	$370.32				70
				9		EAR99	PE-W137S001-9	$405.03				71
					CPR-137G	EAR99	PE-W137S002-9	$381.40				72
				12	Round Cover UG-344/U	EAR99	PE-W137S001-12	$418.53				73
					CPR-137G	EAR99	PE-W137S002-12	$436.45				74
WRD-180	18 - 40	0.4	1.25:1	3	Square Cover UG	EAR99	PEWRD180S001-3	$602.66				75
		0.5		6		EAR99	PEWRD180S001-6	$1,009.85				76
WRD-650	6.5 - 18	0.3	1.15:1	3		EAR99	PEWRD650S001-3	$537.50				77
		0.4		6		EAR99	PEWRD650S001-6	$912.12				78
WRD-750	7.5 - 18	0.3		3		EAR99	PEWRD750S001-3	$537.50				79
		0.4		6		EAR99	PEWRD750S001-6	$912.12				80

WAVEGUIDE TERMINATIONS

Waveguide Type	RF Frequency (GHz.)	Input Power (Watts)	Max VSWR	Length (in)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
WR-10	75 - 110	0.4	1.06:1	2	Round Cover UG-387/U	EAR99	PEW10TR0001	$557.93		See Web for Volume Pricing		81
		0.4	1.25:1		Round Cover UG-387/U-Mod	EAR99	PE-W10TR1001	$588.37				82
WR-12	60 - 90	0.6	1.2:1		Round Cover UG-387/U	EAR99	PE-W12TR1001	$570.31				83
WR-15	50 - 75	1	1.2:1		Round Cover UG-385/U	EAR99	PEW15TR0001	$599.02				84
WR-19	40 - 60	2	1.06:1		Round Cover UG-383/U	EAR99	PEW19TR0001	$502.93				85
		2	1.09:1		Round Cover UG-383/U-Mod	EAR99	PE-W19TR1001	$530.38				86
WR-22	33 - 50	4	1.05:1		Round Cover UG-383/U	EAR99	PE-W22TR1002	$518.28				87
WR-28	26.5 - 40	0.5	1.3:1	1	Square Cover UG-599/U	EAR99	PE6800	$485.38				88
		0.5	1.05:1	2	Square Cover	EAR99	PE6809	$925.09				89
		0.5	1.02:1		Square Cover UG-599/U	EAR99	PEWTR1000	$716.65				90
		1	1.03:1	2	Square Cover UG-599/U	EAR99	PE-W28TR1003	$532.13				91
	29.4 - 31	2	1.15:1	1	Square Cover UG-599/U	EAR99	PE-W28TR1002	$374.46				92
	26.5 - 40	40	1.07:1	3	Square Cover	EAR99	PE6818	$1,006.58				93
		50	1.25:1	4	Square Cover UG-599/U	EAR99	PE-W28TR1004	$886.88				94
		100	1.25:1	5	Square Cover UG-599/U	EAR99	PE-W28TR1005	$1,478.13				95
WR-34	22 - 33	0.5	1.25:1	1	Square Cover	EAR99	PE6801	$384.32				96
		0.5	1.05:1	3	Square Cover	EAR99	PE6810	$889.49				97
	19.6 - 21.2	1	1.15:1	1	Square Cover UG-597/U	EAR99	PE-W34TR1001	$413.88				98
	22 - 33	1	1.25:1		Square Cover UG-1530/U	EAR99	PEWTR1001	$627.29				99
		45	1.1:1	4	Square Cover	EAR99	PE6819	$1,422.00				1
		75	1.1:1		Square Cover	EAR99	PE6828	$1,319.98				2
WR-42	18 - 26.5	0.5	1.25:1	1	Square Cover UG-597/U	EAR99	PE6802	$471.63				3
		0.5	1.05:1	3	Square Cover	EAR99	PE6811	$1,047.79				4
	19.6 - 21.2	1	1.15:1	1	Square Cover UG-597/U	EAR99	PE-W42TR1002	$374.46				5
	18 - 26.5	1	1.02:1		Square Cover UG-595/U	EAR99	PEWTR1002	$622.15				6
		6	1.08:1	3	Square Cover UG-595/U	EAR99	PE-W42TR1001	$559.12				7
		50	1.07:1	4	Square Cover	EAR99	PE6820	$938.93				8
		100	1.1:1		Square Cover	EAR99	PE6829	$997.21				9
WR-51	15 - 18	1	1.2:1	1	Square Cover	EAR99	PE6803	$432.67				10
	15 - 22	1	1.05:1	3	Square Cover	EAR99	PE6812	$1,082.72				11
		1	1.02:1		Square Cover	EAR99	PEWTR1003	$645.78				12

WAVEGUIDE TERMINATIONS





Waveguide Type	RF Frequency (GHz.)	Input Power (Watts)	Max VSWR	Length (in)	Flange Type	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
WR-62	14.5 - 17.8	1	1.05:1	1	Square Cover UG-1665/U	EAR99	PE-W62TR1003	$453.29		See Web for Volume Pricing		13
	12.4 - 18	1.5	1.02:1		Square Cover UG-419/U	EAR99	PEWTR1004	$606.38				14
	11.9 - 18	2	1.03:1	4	Square Cover		PE6201A	$536.43				15
	12.4 - 18	2	1.2:1	1	Square Cover	EAR99	PE6804	$486.35				16
		60	1.07:1	4	Square Cover	EAR99	PE6836	$971.89				17
WR-75	10 - 15	2	1.2:1	1	Square Cover	EAR99	PE6805	$724.47				18
		2	1.05:1	4	Square Cover	EAR99	PE6814	$874.79				19
		2.5	1.02:1		Square Cover	EAR99	PEWTR1005	$653.06				20
		75	1.07:1	5	Square Cover	EAR99	PE6823	$965.35				21
		175	1.1:1	6	Square Cover	EAR99	PE6832	$1,472.62				22
WR-90	8.2 - 12.4	2	1.2:1	1	Square Cover UG-135/U	EAR99	PE6806	$524.94				23
		2	1.05:1	4	Square Cover	EAR99	PE6815	$841.14				24
	9 - 10	2	1.05:1	1	Square Cover UG-135/U	EAR99	PE-W90TR1001	$492.71				25
	8.2 - 12.4	4	1.02:1		Square Cover UG-39/U	EAR99	PEWTR1006	$598.53				26
		4	1.02:1		CPR-90G	EAR99	PEWTR1007	$610.35				27
	8.2 - 12.5	50	1.25:1	4	Square Cover UG-135/U	EAR99	PE-W90TR1002	$1,103.66				28
	8.2 - 12.4	90	1.07:1	6	Square Cover	EAR99	PE6824	$1,245.89				29
		200	1.1:1		Square Cover	EAR99	PE6833	$1,639.32				30
WR-102	7 - 11	300	1.1:1	7	Square Cover	EAR99	PE6834	$1,677.04				31
WR-112	7.05 - 10	2	1.2:1	1	Square Cover	EAR99	PE6808	$444.80				32
		5	1.02:1		Square Cover UG-51/U	EAR99	PEWTR1008	$637.89				33
		5	1.02:1		CPR-112G	EAR99	PEWTR1009	$690.97				34
		300	1.1:1	7	Square Cover UG-51/U	EAR99	PE6835	$2,266.17				35
WR-137	5.85 - 8.2	6	1.02:1		Round Cover UG-344/U	EAR99	PEWTR1010	$673.32				36
		6	1.02:1		CPR-137G	EAR99	PEWTR1011A	$665.15				37
	5.38 - 8.17	500	1.25:1	14	CPR-137F	EAR99	PE-W137TR1001	$2,601.50				38
WR-159	4.64 - 7.05	5	1.03:1	8	CPR-159F	EAR99	PE-W159TR1002	$670.08				39
	4.8 - 5.2	50	1.2:1	4	CPR-159F	EAR99	PE-W159TR1001	$1,241.63				40
WR-187	3.94 - 5.99	5	1.03:1	9	CPR-187F	EAR99	PE-W187TR1002	$591.25				41
	4.4 - 5	70	1.1:1	3	CPR-187F	EAR99	PE-W187TR1001	$709.50				42
WR-229	3.22 - 4.9	5	1.03:1	10	CPR-229F	EAR99	PE-W229TR1001	$788.33				43
		5	1.2:1	3	CPR-229F	EAR99	PE-W229TR1002	$867.16				44
WR-284	2.6 - 3.95	5	1.03:1	12	CPR-284F	EAR99	PE-W284TR1001	$1,103.66				45
WRD-180	18 - 40	0.5	1.15:1	4	Square Cover UG	EAR99	PEWRD180TR1000	$1,417.05				46
WRD-650	6.5 - 18	1	1.15:1		Square Cover UG	EAR99	PEWRD650TR1000	$1,075.00				47
WRD-750	7.5 - 18	1	1.15:1		Square Cover UG	EAR99	PEWRD750TR1000	$1,075.00				48

WAVEGUIDE TRANSITIONS

WG 1 Type	Flange 1 Type	WG 2 Type	Flange 2 Type	VSWR	ECCN	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
WR-10	Round Cover UG-387/U-Mod	WR-12	Round Cover UG-387/U	1.6:1	EAR99	PE-W10TS12001A	$1,328.18		See Web for Volume Pricing		49
		WR-15	Round Cover UG-385/U	1.45:1	EAR99	PE-W10TS15001	$1,321.63				50
		WR-19	Round Cover UG-383/U-Mod	1.4:1	EAR99	PE-W10TS19001	$1,363.82				51
WR-12	Round Cover UG-387/U	WR-15	Round Cover UG-385/U	1.2:1	EAR99	PE-W12TS15001	$1,374.49				52
WR-15	Round Cover UG-385/U	WR-19	Round Cover UG-383/U-Mod	1.1:1	EAR99	PE-W15TS19001	$1,374.49				53
		WR-22	Round Cover UG-383/U	1.15:1	EAR99	PE-W15TS22001	$1,363.82				54
WR-19	Round Cover UG-383/U-Mod	WR-22		1.5:1	EAR99	PE-W19TS22001	$1,321.63				55
		WR-28	Square Cover UG-599/U	1.35:1	EAR99	PE-W19TS28001	$1,374.49				56
WR-22	Round Cover UG-383/U	WR-28		1.35:1	EAR99	PE-W22TS28001	$1,374.49				57
		WR-42	Square Cover UG-595/U	1.35:1	EAR99	PE-W22TS42001	$1,253.25				58
WR-28	Square Cover UG-599/U	WR-42		1.2:1	EAR99	PE-W28TS42001	$1,253.25				59
		WR-51	UBR-180/U-Mod	1.38:1	EAR99	PE-W28TS51001	$1,438.22				60
WR-34	Square Cover UG-1530/U	WR-28	Square Cover UG-599/U	1.08:1	EAR99	PEWTS1010	$841.79				61
WR-42	Square Cover UG-595/U	WR-34	Square Cover UG-1530/U	1.08:1	EAR99	PEWTS1009	$816.31				62
WR-62	Square Cover UG-1665/U	WR-51	Square Cover	1.08:1	EAR99	PEWTS1007A	$837.24				63

WAVEGUIDE TRANSITIONS

WG 1 Type	Flange 1 Type	WG 2 Type	Flange 2 Type	VSWR	ECCN	Model No	1-4	5-9	10-24	25+	ROW
WR-75	Square Cover	WR-62	Square Cover UG-1665/U	1.08:1	EAR99	PEWTS1006	$882.92	$838.77	$794.63	$759.31	64
WR-90	Square Cover UG-39/U	WR-75	Square Cover	1.08:1	EAR99	PEWTS1004	$894.66	$849.93	$805.19	$769.41	65
	CPR-90G	WR-75		1.08:1	EAR99	PEWTS1005A	$888.99	$844.54	$800.09	$764.53	66
WR-112	Square Cover UG-51/U	WR-90	Square Cover UG-39/U	1.08:1	EAR99	PEWTS1002	$946.89	$899.55	$852.20	$814.33	67
	CPR-112G	WR-90	CPR-90G	1.08:1	EAR99	PEWTS1003	$898.78	$853.84	$808.90	$772.95	68
WR-137	Round Cover UG-344/U	WR-112	Square Cover UG-51/U	1.08:1	EAR99	PEWTS1000	$1,012.20	$961.59	$910.98	$870.49	69
	CPR-137G	WR-112	CPR-112G	1.08:1	EAR99	PEWTS1001	$1,018.75	$967.81	$916.88	$876.13	70

WAVEGUIDE TWISTS

WG Type	RF Freq. (GHz.)	Max VSWR	WG Offset Angle (Deg)	Length (in)	Flange Type	ECCN	Model No	1-9	10-24	25-49	50+	ROW
WR-10	75 - 110	1.1:1	45 Left-hand	1	Round Cover UG-387/U-Mod	EAR99	PE-W10TW1002	$456.33	$433.51	$410.70	$392.44	71
			45 Right-hand		Round Cover UG-387/U-Mod	EAR99	PE-W10TW1003	$449.59	$427.11	$404.63	$386.65	72
		1.43:1	90		Round Cover UG-387/U-Mod	EAR99	PE-W10TW1001	$430.35	$408.83	$387.32	$370.10	73
WR-12	60 - 90	1.16:1	45 Left-hand		Round Cover UG-387/U	EAR99	PE-W12TW1002	$456.33	$433.51	$410.70	$392.44	74
			45 Right-hand		Round Cover UG-387/U	EAR99	PE-W12TW1003	$456.33	$433.51	$410.70	$392.44	75
			90 Right-hand		Round Cover UG-387/U-Mod	EAR99	PEW12TW001	$510.49	$484.97	$459.44	$439.02	76
		1.12:1	90		Round Cover UG-387/U	EAR99	PE-W12TW1001	$510.49	$484.97	$459.44	$439.02	77
WR-15	50 - 75	1.11:1	45 Left-hand	2	Round Cover UG-385/U	EAR99	PE-W15TW1002	$449.59	$427.11	$404.63	$386.65	78
			45 Right-hand		Round Cover UG-385/U	EAR99	PE-W15TW1003	$456.33	$433.51	$410.70	$392.44	79
			90		Round Cover UG-385/U	EAR99	PE-W15TW1001	$430.35	$408.83	$387.32	$370.10	80
WR-19	40 - 60	1.25:1	45 Left-hand		Round Cover UG-383/U-Mod	EAR99	PE-W19TW1002	$449.59	$427.11	$404.63	$386.65	81
			45 Right-hand		Round Cover UG-383/U-Mod	EAR99	PE-W19TW1003	$449.59	$427.11	$404.63	$386.65	82
		1.22:1	90		Round Cover UG-383/U-Mod	EAR99	PE-W19TW1001	$396.25	$376.44	$356.63	$340.78	83
WR-22	33 - 50	1.02:1	45 Left-hand		Round Cover UG-383/U	EAR99	PE-W22TW1002	$449.59	$427.11	$404.63	$386.65	84
			45 Right-hand		Round Cover UG-383/U	EAR99	PE-W22TW1003	$449.59	$427.11	$404.63	$386.65	85
		1.15:1	90		Round Cover UG-383/U	EAR99	PEW22TW001	$396.25	$376.44	$356.63	$340.78	86
		1.02:1	90		Round Cover UG-383/U	EAR99	PE-W22TW1001	$402.18	$382.07	$361.96	$345.87	87
WR-28	26.5 - 40	1.1:1	45 Right-hand		Square Cover UG-595/U	EAR99	PEW28TW001	$481.07	$457.02	$432.96	$413.72	88
		1.09:1	45 Left-hand		Square Cover UG-599/U	EAR99	PE-W28TW1002	$488.27	$463.86	$439.44	$419.91	89
			45 Right-hand		Square Cover UG-599/U	EAR99	PE-W28TW1003	$488.27	$463.86	$439.44	$419.91	90
		1.07:1	90		Square Cover UG-599/U	EAR99	PE-W28TW1001	$402.18	$382.07	$361.96	$345.87	91
WR-42	18 - 26.5	1.25:1	45 Left-hand	3	Square Cover UG-595/U	EAR99	PE-W42TW1002	$475.67	$451.89	$428.10	$409.08	92
			45 Right-hand		Square Cover UG-595/U	EAR99	PE-W42TW1003	$475.67	$451.89	$428.10	$409.08	93
		1.07:1	90		Square Cover UG-595/U	EAR99	PE-W42TW1001	$419.57	$398.59	$377.61	$360.83	94
WRD-750	7.5 - 18	1.25:1	90	8	Square Cover UG	EAR99	PEWRD750TW1001	$912.12	$866.51	$820.91	$784.42	95
WRD-180	18 - 40	1.35:1	90	3	Square Cover UG	EAR99	PEWRD180TW1001	$1,009.85	$959.36	$908.87	$868.47	96
WR-8	90 - 140		45 Right-hand	1	Square Cover UG-387/U-Mod	EAR99	PEW8TW0000	$544.46	$517.24	$490.01	$468.24	97
			45 Left-hand		Square Cover UG-387/U-Mod	EAR99	PEW8TW0001	$536.43	$509.61	$482.79	$461.33	98
			90 Right-hand		Round Cover UG-387/U-Mod	EAR99	PEW8TW0002	$536.43	$509.61	$482.79	$461.33	99
WR-6	110 - 170		45 Right-hand		Square Cover UG-387/U-Mod	EAR99	PEW6TW0000	$544.46	$517.24	$490.01	$468.24	1
			45 Left-hand		Square Cover UG-387/U-Mod	EAR99	PEW6TW0001	$536.43	$509.61	$482.79	$461.33	2
			90 Right-hand		Round Cover UG-387/U-Mod	EAR99	PEW6TW0002	$544.46	$517.24	$490.01	$468.24	3
WR-5	140 - 220		45 Right-hand		Square Cover UG-387/U-Mod	EAR99	PEW5TW0000	$577.19	$548.33	$519.47	$496.38	4
			45 Left-hand		Square Cover UG-387/U-Mod	EAR99	PEW5TW0001	$568.68	$540.25	$511.81	$489.06	5
			90 Right-hand		Round Cover UG-387/U-Mod	EAR99	PEW5TW0002	$568.68	$540.25	$511.81	$489.06	6
WRD-650	6.5 - 18		90	8	Square Cover UG	EAR99	PEWRD650TW1001	$912.12	$866.51	$820.91	$784.42	7

WAVEGUIDE VARIABLE ATTENUATORS



Waveguide Type	RF Frequency (GHz.)	Flange Type	IL (dB)	Max Atten. (dB)	ECCN	Model No	1	2-4	5-9	10+	ROW
WR-10	75 - 110	Round Cover UG-387/U-Mod	1	30	EAR99	PE-W10AT002-30	$2,029.41	$1,948.23	$1,867.06	$1,785.88	8
WR-12	60 - 90	Round Cover UG-387/U	0.4		EAR99	PE-W12AT002-30	$2,098.22	$2,014.29	$1,930.36	$1,846.43	9
WR-15	50 - 75	Round Cover UG-385/U	0.8		EAR99	PE-W15AT001-30	$2,098.22	$2,014.29	$1,930.36	$1,846.43	10
WR-19	40 - 60	Round Cover UG-383/U-Mod	0.6		EAR99	PE-W19AT001-30	$2,048.32	$1,966.39	$1,884.45	$1,802.52	11
WR-22	33 - 50	Round Cover UG-383/U	0.5		EAR99	PE-W22AT001-30	$2,008.15	$1,937.86	$1,867.58	$1,807.34	12

WAVEGUIDE ACCESSORIES

Waveguide Type	Description	Model No	1 Pc. Price	See Web for Volume Pricing	ROW
WR-10	WR-10 Waveguide Shim, UG-Cover Round flange, 2mm Brass	PEW10FS2	$117.18	See Web for Volume Pricing	13
	WR-10 Waveguide Short Plate, UG-Cover Round Flange, 4mm Copper	PEW10SP4	$106.15		14
WR-12	WR-12 Waveguide Shim, UG-Cover Round flange, 2mm Brass	PEW12FS2	$106.15		15
	WR-12 Waveguide Short Plate, UG-Cover Round Flange, 4mm Copper	PEW12SP4	$117.18		16
WR-15	WR-15 Waveguide Shim, UG-Cover Round flange, 2mm Brass	PEW15FS2	$106.15		17
	WR-15 Waveguide Short Plate, UG-Cover Round Flange, 4mm Copper	PEW15SP4	$106.15		18
WR-19	WR-19 Waveguide Shim, UG-Cover Round flange, 3mm Brass	PEW19FS3	$106.15		19
	WR-19 Waveguide Short Plate, UG-Cover Round Flange, 4mm Copper	PEW19SP4	$106.15		20
WR-22	WR-22 Waveguide Shim, UG-Cover Round flange, 3mm Brass	PEW22FS3	$106.15		21
	WR-22 Waveguide Short Plate, UG-Cover Round Flange, 4mm Copper	PEW22SP4	$106.15		22
WR-28	WR-28 Waveguide Electrically Conductive Gasket kit Square Cover, Choke Flange	PEWGK1014	$115.66		23
	WR-28 Waveguide Gasket kit Square Cover, Choke Flange, Non-Conductive	PEWGK1000	$49.46		24
	WR-28 Waveguide Shim, UG-Cover Square flange, 3mm Brass	PEW28FS3	$139.58		25
	WR-28 Waveguide Short Plate, UG-Cover Square Flange, 5mm Copper	PEW28SP4	$139.58		26
WR-34	WR-34 Waveguide Shim, UG-Cover Square flange, 4mm Brass	PEW34FS4	$139.58		27
	WR-34 Waveguide Short Plate, UG-Cover Square Flange, 4mm Copper	PEW34SP4	$139.58		28
WR-42	WR-42 Waveguide Shim, UG-Cover Square flange, 4mm Brass	PEW42FS4	$136.17		29
	WR-42 Waveguide Short Plate, UG-Cover Square Flange, 4mm Copper	PEW42SP4	$160.18		30
WR-42,	WR-42, WR-34 Waveguide Electrically Conductive Gasket kit Square Cover, Choke Flange	PEWGK1015	$133.30		31
WR-42	WR-42, WR-34 Waveguide Gasket kit Square Cover, Choke Flange, Non-Conductive	PEWGK1001	$47.88		32
WR-51	WR-51 Waveguide Electrically Conductive Gasket kit Square Cover, Choke Flange	PEWGK1016	$144.44		33
	WR-51 Waveguide Gasket kit Square Cover, Choke Flange, Non-Conductive	PEWGK1002	$48.03		34
WR-62	WR-62 Waveguide Electrically Conductive Gasket kit Square Cover, Choke Flange	PEWGK1017	$211.09		35
	WR-62 Waveguide Gasket kit Square Cover, Choke Flange, Non-Conductive	PEWGK1003	$54.67		36
	WR-62 Waveguide Shim, UG-Cover Square flange, 5mm Brass	PEW62FS5	$70.77		37
	WR-62 Waveguide Short Plate, UG-Cover Square Flange, 5mm Copper	PEW62SP5	$88.46		38
WR-75	WR-75 Waveguide Electrically Conductive Gasket kit Square Cover, Choke Flange	PEWGK1018	$133.03		39
	WR-75 Waveguide Gasket kit Square Cover, Choke Flange, Non-Conductive	PEWGK1004	$54.67		40
	WR-75 Waveguide Shim, UG-Cover Square flange, 5mm Brass	PEW75FS5	$74.31		41
	WR-75 Waveguide Short Plate, UG-Cover Square Flange, 5mm Copper	PEW75SP5	$88.46		42

WAVEGUIDE ACCESSORIES

Waveguide Type	Description	Model No	1 Pc. Price	See Web for Volume Pricing			ROW
WR-90	WR-90 Waveguide Electrically Conductive Gasket kit Square Cover, Choke Flange	PEWGK1019	$186.51				43
	WR-90 Waveguide Electrically Conductive Gasket kit, CPR Flat Flange	PEWGK1021	$135.29				44
	WR-90 Waveguide Electrically Conductive Gasket kit, CPR Grooved Flange	PEWGK1020	$156.20				45
	WR-90 Waveguide Gasket kit Square Cover, Choke Flange, Non-Conductive	PEWGK1005	$58.27				46
	WR-90 Waveguide Gasket kit, CPR90 Flat Flange, Non-Conductive	PEWGK1007	$65.68				47
	WR-90 Waveguide Gasket kit, CPR90 Grooved Flange, Non-Conductive	PEWGK1006	$65.68				48
	WR-90 Waveguide Shim, UG-Cover Square flange, 5mm Brass	PEW90FS5	$74.31				49
	WR-90 Waveguide Short Plate, UG-Cover Square Flange, 5mm Brass	PEW90SP5	$103.45				50
WR-112	WR-112 Waveguide Electrically Conductive Gasket kit Square Cover, Choke Flange	PEWGK1022	$161.96				51
	WR-112 Waveguide Electrically Conductive Gasket kit, CPR Flat Flange	PEWGK1024	$146.11				52
	WR-112 Waveguide Electrically Conductive Gasket kit, CPR Grooved Flange	PEWGK1023	$202.89				53
	WR-112 Waveguide Gasket kit Square Cover, Choke Flange, Non-Conductive	PEWGK1008	$58.27				54
	WR-112 Waveguide Gasket kit, CPR112 Flat Flange, Non-Conductive	PEWGK1010	$67.65				55
	WR-112 Waveguide Gasket kit, CPR112 Grooved Flange, Non-Conductive	PEWGK1009	$67.65				56
	WR-112 Waveguide Shim, UG-Cover Square flange, 5mm Brass	PEW112FS5	$88.46				57
	WR-112 Waveguide Short Plate, UG-Cover Square Flange, 5mm Copper	PEW112SP5	$88.46				58
WR-137	WR-137 Waveguide Electrically Conductive Gasket kit, CPR Grooved Flange	PEWGK1026	$190.48				59
	WR-137 Waveguide Electrically Conductive Gasket kit, CPR Grooved Flange	PEWGK1027	$161.96				60
	WR-137 Waveguide Electrically Conductive Gasket kit, Round Cover, Choke Flange	PEWGK1025	$316.15				61
	WR-137 Waveguide Gasket kit Round Cover, Choke Flange, Non-Conductive	PEWGK1011	$59.53	See Web for Volume Pricing			62
	WR-137 Waveguide Gasket kit, CPR137 Flat Flange, Non-Conductive	PEWGK1013	$62.80				63
	WR-137 Waveguide Gasket kit, CPR137 Grooved Flange, Non-Conductive	PEWGK1012	$69.76				64
	WR-137 Waveguide Shim, CPR-137F flange, 7mm Brass	PEW137FS7	$108.94				65
	WR-137 Waveguide Short Plate, CPR-137F Flange, 7mm Copper	PEW137SP7	$106.15				66
WR-159	WR-159 Waveguide Shim, CPR-159F flange, 7mm Aluminum	PEW159FS7	$88.46				67
	WR-159 Waveguide Short Plate, CPR-159F Flange, 7mm Aluminum	PEW159SP7	$88.46				68
WR-187	WR-187 Waveguide Shim, CPR-187F flange, 7mm Aluminum	PEW187FS7	$88.46				69
	WR-187 Waveguide Short Plate, CPR-187F Flange, 7mm Aluminum	PEW187SP7	$88.46				70
WR-284	WR-284 Waveguide Shim, CPR-284F flange, 8mm Aluminum	PEW284FS8	$106.15				71
	WR-284 Waveguide Short Plate, CPR-284F Flange, 8mm Aluminum	PEW284SP8	$106.15				72
WR-340	WR-340 Waveguide Shim, CPR-340F flange, 10mm Aluminum	PEW340FS10	$125.62				73
	WR-340 Waveguide Short Plate, CPR-340F Flange, 10mm Aluminum	PEW340SP10	$181.41				74
WR-430	WR-430 Waveguide Shim, CPR-430F flange, 10mm Aluminum	PEW430FS10	$125.62				75
	WR-430 Waveguide Short Plate, CPR-430F Flange, 10mm Aluminum	PEW430SP10	$180.60				76
	0.75 inch Diameter Flange, Standard Antenna Mounting Fixture with UG-385/U and UG-387/U Flanges	PEWAM0000	$564.38				77
	0.75 inch Square Flange, Standard Antenna Mounting Fixture with UG-599/U Flanges	PEWAM0001	$564.38				78
	0.88 inch Square Flange, Standard Antenna Mounting Fixture with UG-595/U and UG-1530/U Flanges	PEWAM0002	$564.38				79
	1.125 inch Diameter Flange, Standard Antenna Mounting Fixture with UG-383/U Flanges	PEWAM0003	$572.83				80
	4-40 with 3/32 inch Hex, Stainless Steel Waveguide Flange Screw	PEWGHW9000	$5.13				81
	Waveguide Table Jack, Large	PEWGHW1001	$374.09				82
	Waveguide Table Jack, Medium	PEWGHW1000	$323.91				83

INDEX GUIDE TO
APPENDIX

APPENDIX.....390

PASTERNACK REACH PROGRAM.....391

PASTERNACK RoHS PROGRAM.....391

MAILING LIST CHANGES.....392

BINDING TERMS.....392

PE PART # INDEX.....395

CONVERSION TABLES.....407

MOUNTING HOLES.....409

CONNECTOR IDENTIFIER.....410

CONNECTOR FREQUENCY RANGE CHART.....414

PASTERNACK ENTERPRISES – REACH PRODUCT COMPLIANCE PROGRAM

OUR COMMITMENT

At Infinite Electronics, we maintain a comprehensive REACH compliance program to help customers with their green aspirations. We strive to have accurate and available material content data on all of our products. When data is not yet available, customer requests will be given top priority.

WHAT IS REACH?

Regulation (EC) No. 1907/2006 of the European Parliament and of the Council of 18 December 2006 is commonly referred to as REACH (Registration, Evaluation, Authorization, and Restriction of Chemicals). The REACH regulation became effective on June 1, 2007 with the objective to improve protection of human health and the environment from exposure to chemicals. Under REACH, there is an obligation to ensure that articles do not contain any of the substances on the REACH Substances of Very High Concern (SVHCs) Candidate list in concentrations greater than 0.1% by weight. SVHCs are substances that may cause cancer or other serious health or environmental effects and thus face potential restriction or outright bans. The SVHC list is updated with additional substances at approximately every six months, thus product declarations must indicate the applicable SVHC release date.

OUR APPROACH

Infinite Electronics has partnered with Assent Compliance, a world class provider of compliance software and professional support staff, to obtain current material content data on our vast selection of electronic products. Together, we work with our supply chain to routinely collect and analyze this data which enables us to determine the state of compliance for each item we sell. As part of our process integration efforts, we are currently redesigning the way this data can be found on-line so that it is consistent across all brands. Once deployed, we will have a customer self-serve search engine tool to enable real-time creation of part number specific declarations. Until then, customers may request declarations directly from our Assent Compliance partners at InfiniteElectronicsRequests@assentcompliance.com. Please ensure you that you list all Infinite Electronics part numbers within your request.

PASTERNACK ENTERPRISES ROHS COMPLIANCE PROGRAM

Lead-free solder is now available for all cable assemblies upon request or online at www.Pasternack.com.

OUR COMMITMENT

At Infinite Electronics, we maintain a comprehensive RoHS compliance program to help customers with their green aspirations. We strive to have accurate and available material content data on all of our products. When data is not yet available, customer requests will be given top priority.

WHAT IS ROHS?

Short for Directive on the restriction of the use of certain hazardous substances in electrical and electronic equipment, RoHS was adopted in February 2003 by the European Union. Now in its third iteration as (EU) Directive 2015/863, RoHS guidelines and legislation are intended to reduce the presence of ten (10) materials deemed hazardous to the environment. To comply, products entering the EU must not have a homogeneous presence of these materials above the following levels by percentage of their weight:

- Lead (Pb) < 0.1%
- Mercury (Hg) < 0.1%
- Cadmium (Cd) < 0.01%
- DEHP < 0.1%
- DBP < 0.1%
- Hexavalent Chromium (CrVI) < 0.1%
- Polybrominated Biphenyls (PBB) < 0.1%
- Polybrominated Diphenyl Esters (PBDE) < 0.1%
- BBP < 0.1%
- DIBP < 0.1%

OUR APPROACH

Infinite Electronics has partnered with Assent Compliance, a world class provider of compliance software and professional support staff, to obtain current material content data on our vast selection of electronic products. Together, we work with our supply chain to routinely collect and analyze this data which enables us to determine the state of compliance for each item we sell. As part of our process integration efforts, we are currently redesigning the way this data can be found on-line so that it is consistent across all brands. Once deployed, we will have a customer self-serve search engine tool to enable real-time creation of part number specific declarations. Until then, customers may request declarations directly from our Assent Compliance partners at InfiniteElectronicsRequests@assentcompliance.com. Please ensure you that you list all Infinite Electronics part numbers within your request.

MAILING LIST CHANGES

If you receive more than one RF Product Guide with the same name and address, please notify Pasternack and pass the RF Product Guide along to a friend. Also, if you do not require multiple copies to the same company address, contact a sales representative to verify and modify your mailing information. A forms-based communications method to add, delete or modify mailing information is available at www.pasternack.com. By clicking "Contact Us", and then clicking "Remove Name from Mailing List", you may complete the form to request a change to your mailing preferences. In addition, by clicking "RF Product Guide", and then clicking "Request a Printed RF Product Guide", you may add your contact information to our mailing list. Please note service opt-in and opt-out options located on the forms. Alternatively, you may mail, email, telephone or fax Pasternack your request.

PLACING YOUR ORDER

► **BY TELEPHONE: 866-PASTERNACK (866-727-8376)**
US & CANADA, OR 949-261-1920

Our friendly sales representatives are ready to serve you from 5:00am to 5:30pm Pacific Standard Time (PST), Monday through Friday. For the most efficient service, please have ready a list of quantities and part numbers and, if paying by credit card, your MasterCard, VISA, American Express or Discover card. Note: Calls may be recorded or monitored for quality and training purposes.

► **BY FAX: 949-261-7451**

Our fax lines can be accessed 7 days a week, 24 hours a day. Orders received after 4:00pm PST will be promptly processed and shipped the next business day. Please include your daytime phone number and/or email address in case we have any questions about your order.

► **BY INTERNET: WWW.PASTERNACK.COM**
OR EMAIL: SALES@PASTERNACK.COM

Order online 7 days a week, 24 hours a day using our online ordering system. Just search for the items you want and add them to your shopping cart. Internet orders entered after 4:00 pm PST will be promptly processed and shipped the next business day.

► **BY MAIL: SIMPLY MAIL YOUR ORDER TO:**
PASTERNACK ENTERPRISES.
17802 FITCH
PO BOX 16759
IRVINE, CA 92623-6759 USA

International customers, please see "International Orders" below for additional information.

TERMS AND CONDITIONS OF SALE:

The following from Pasternack's Binding Terms and Conditions of Sale are provided for your convenience. A complete documentation of the Binding Terms and Conditions of Sale may be found in the back of the RF Product Guide, or on Pasternack's website at https://www.pasternack.com/t-terms-of-sale.aspx. Any questions or clarifications may be answered by contacting Customer Service at (+1) 949-261-1920 or by any of the methods listed above.

NO MINIMUM ORDER REQUIREMENT

GROUND FREIGHT:

Shipping or freight charges and insurance will be paid by the customer. All sales are made FCA-Shipping Point (as defined by the INCOTERMS 2000) in Irvine, CA USA & Lewisville, TX USA. Shipping or freight charges from Pasternack's Irvine, CA factory are prepaid and added to the invoice or billed collect.

SAME-DAY SHIPMENT:

Same-day shipment will apply to orders received Monday through Friday, prior to 4:00pm PST.
- All UPS air and surface options
- All FedEx air options (with an approved account number)
- Most other shipping options, including DHL (with an approved account number) and USPS

COUNTER-TO-COUNTER SHIPPING:

For your urgent order requiring our fastest shipping method, we will place your order on the next available flight from Santa Ana-Orange County John Wayne International Airport (Airport code: SNA) and Dallas/Fort Worth International Airport (Airport Code: DFW) to the destination you specify. Please call for details.

PAYMENT TERMS:

Pasternack offers a number of convenient payment methods:

For United States customers, we offer check, money order, MasterCard, VISA, American Express, and Discover. as well as open account credit to qualified institutions and businesses. Payment must be made in US Dollars.

For Canadian customers, we offer all of the above payment options.
For International customers, see International Orders.

OPEN ACCOUNT CREDIT:

Net 30 Days terms are available to businesses, schools and agencies subject to credit approval. Approval can begin by submitting a completed Credit Application, which can be found online at: www.Pasternack.com/t-CreditApplication.aspx

EFT/WIRE TRANSFERS:

Please contact us for details. We will inform you of the total amount which will include shipping charges and any applicable wire transfer fees. Orders will not be accepted until funds have been received in full.

WELLS FARGO BANK
420 MONTGOMERY ST.
SAN FRANCISCO, CA 94104 USA
ACCOUNT NUMBER: 4270 0000 0000 0000 1
ROUTING NUMBER: 121000248
SWIFT NUMBER: WFBIUS6S

INTERNATIONAL ORDERS:

In addition to the United States and its territories, Pasternack accepts international orders. All orders of international origin are exported from the US in accordance with the Export Administration Regulations. Diversion contrary to US Law is prohibited. Please see Pasternack's Binding Terms and Conditions of Sale for full details.

Pasternack has international distributors for the following countries:
Africa: Namibia, South Africa
Asia-Pacific: Australia, China PRC, India, Indonesia, Japan, Malaysia, New Zealand, Singapore, South Korea, Thailand
Europe: Austria, Belgium, Czech Republic, Denmark, Finland, France, Germany, Ireland, Italy, Kazakhstan, Luxembourg, Netherlands, Norway, Poland, Portugal, Russia, Slovakia, Spain, Sweden, Switzerland, Turkey, United Kingdom
Middle East: Israel
South America: Brazil

To access their complete contact information, please see our International Distributors section in this RF Product Guide. (inside back cover)

INTERNATIONAL SHIPPING CHARGES:

Shipping or freight charges and insurance will be paid by the customer. All sales are made FCA-Shipping Point (as defined by the INCOTERMS 2000) in Irvine, CA USA. We ship orders by UPS, FedEx (with an approved account number), or DHL (with approved account number) with delivery in 2 to 3 days to most locations worldwide.

INTERNATIONAL TAXES AND DUTIES:

Customer is responsible for duties and taxes.

BINDING TERMS AND CONDITIONS OF SALE

1. SCOPE; CHANGES

The terms and conditions stated herein (this "Agreement") govern all sales of products or services ("products") by Infinite Electronics, Inc. (collectively, "we," "us," "our," or "seller") to you or the entity you represent ("you" or "buyer"). You represent to us that you are lawfully able to enter into contracts (e.g., you are not a minor) and that if you are entering into this Agreement for an entity, such as the company you work for, you represent to us that you have the legal authority to bind that entity. Unless otherwise agreed to in writing by seller's authorized agent, any terms and conditions contained in buyer's purchase order or any other document that are different from or in addition to these terms and conditions are objected to, are rejected, and will not be binding on us. By placing an order for products from us, or by accepting delivery of the products described on the applicable packing slip, bill of lading and/or invoice received with the products, you agree to be bound by and accept these terms and conditions of sale.

We may change the terms and conditions of this Agreement in our sole discretion by posting an updated version of these terms and conditions at this location; provided, however, that the terms and condition of this Agreement in effect as of the date of an applicable order shall continue to govern such order and the products purchased thereunder.

2. ORDER ACCEPTANCE

a) Your receipt of an email or other form of order confirmation does not constitute our acceptance of your order or a confirmation of an offer to sell.

b) We reserve the right, without prior notification, to limit the order quantity on any item and/or refuse service to anyone.

c) All orders are subject to review and acceptance by us. You agree to provide complete and accurate contact information in connection with any order submitted to us. Verification of information may be required prior to the acceptance of any order.

d) In the case of pre-stocked finished goods, order acceptance is designated by fulfilling the order. In the case of products requiring post-order processing (including but not limited to design, material purchase, manufacturing or test), order acceptance is designated by performing activities unique to the order.

3. ORDER CANCELLATION

a) Orders fully or partially processed by seller may not be cancelled by buyer.

b) Products not previously stocked as finished goods are both Non-Cancelable and Non-Refundable ("NC/NR"). NC/NR products include cable assemblies, special orders, custom orders, orders for non-standard products, products not customarily in stock, scheduled orders requiring special procurements, or orders for products requiring assembly or manufacturing activities prior to shipping (not stored in completed state) as well as purchased services such as special testing or product modifications.

c) In the event of cancellation or other withdrawal of an order for any reason and without limiting any other remedy as a result of such cancellation or other withdrawal, reasonable cancellation or restocking charges, which shall include all expenses then incurred and commitments made by seller, shall be paid by buyer. Buyer's requests to reschedule are subject to acceptance by seller in its sole discretion. Orders may not be rescheduled after the order has been submitted by seller to the shipment carrier.

4. PRICES

a) Orders are billed at the prices (in US dollars) in effect at the time of shipment.

b) Prices will be as specified within seller's website or as stated in seller's quote / proposal. If no period is specified, quoted prices will be applicable for thirty (30) days.

c) For catalog products, the website contains the most current catalog pricing and is the price reference for such orders. Pricing included in the catalog is for reference only and final pricing is determined by the published website price.

d) For non-catalog products and services, prices cited are based on current costs and are subject to reasonable adjustment on or after the date of acceptance of any purchase order to meet a rise or fall in such costs, as computed on the date of delivery.

e) Prices are subject to change without notice.

f) Prices are exclusive of taxes, impositions and other charges, including: sales, use, excise, value added and similar taxes or charges imposed by any government authority, international shipping charges, forwarding agent's and broker's fees, bank fees, consular fees, document fees and import duties.

5. TERMS OF PAYMENT

a) All payments must be in US Dollars, or will be converted to US Dollars using seller's standard exchange rate at the time of purchase.

b) MasterCard, VISA, Discover, and American Express credit cards, purchase cards and major bank debit cards are accepted. Payment via net thirty (30) days is available to businesses, schools and agencies or as otherwise specified by seller subject to credit approval.

c) For International Orders, MasterCard, VISA, and American Express credit cards are accepted. Payment via open credit account with Net thirty (30) days may be established for companies having three U.S. references accepted to seller. Prepaid Wire Transfer: You can wire the funds to our bank. We will contact you with the total amount, which will include shipping charges and a $40 wire transfer fee. Orders will not be accepted until funds have been received in full and the Purchase Order (PO) has been received. Notwithstanding anything to the contrary in this Agreement, seller may add or remove payment options in seller's sole discretion.

d) Buyer acknowledges that seller has the right to reassess buyer's creditworthiness from time to time. To the extent such is in accordance with law, in the event there is a decline in buyer's creditworthiness, seller may, upon thirty (30) days written notice, revise the payment terms between the parties. Upon request, buyer shall provide financial data evidencing the buyer's worth in order for seller to determine the creditworthiness of buyer. Such information shall include, but not be limited to, annual reports, balance sheets, and bank records.

e) If buyer is delinquent in its payment obligations, without prejudice to any other remedies available to it by law or in equity, seller may demand immediate payment and at seller's option (i) suspend all further deliveries to be made under the purchase order or any further performance under any other contract with buyer or buyer's affiliates, in which event buyer shall not be released in any respect from its obligations to seller under the purchase order; (ii) recover all costs of collection including but not limited to reasonable attorneys' fees; (iii) repossess the product for which payment has not been made; (vi) charge interest at 1.5% per month on the past due amount, not to exceed the interest percentage allowed by law; and (vii) reassess the credit worthiness of buyer and change any current payment terms. Any discount from seller's rates, if any, shall cease to apply to the delinquent invoice, buyer shall be invoiced for such differences in cost, and shall immediately pay the resulting invoice.

6. TAXES AND DUTIES

a) Any taxes related to the products purchased are the responsibility of buyer (excluding taxes based on seller's net income), unless buyer presents an exemption certificate acceptable to seller and the applicable taxing authorities. If any exemption certificate presented by buyer is held to be invalid, then buyer will pay seller the amount of the tax and any penalties and interest related thereto.

b) If possible, seller will bill taxes as a separate item on the invoice presented to buyer.

c) Sales tax will be charged on product cost and shipping & handling where applicable and required by law. Any sales tax due that is not collected by the seller is the responsibility of the buyer.

d) International orders may be subject to various taxes and duties in the country of destination, all of which are the responsibility of the buyer. This includes sales, use, excise, value added and similar taxes or charges imposed by any government authority, international shipping charges, forwarding agent's and broker's fees, bank fees, consular fees, document fees and import duties.

7. SHIPPING COSTS

Shipping or freight charges and insurance will be paid by the buyer and added to the invoice or billed collect unless specifically stated in the quote or order confirmation based on seller practices or promotions.

8. DELIVERY AND TITLE

a) Unless otherwise agreed to in writing, all products are shipped Incoterms 2010 - FCA Shipping Point. Subject to seller's right of stoppage in transit, delivery of the products to the carrier will constitute delivery to buyer and title and risk of loss will pass to buyer.

b) Seller will make reasonable efforts to initiate shipment and schedule delivery as close as possible to buyer's requested delivery date(s). Buyer acknowledges that delivery dates provided by seller are estimates only and that seller will not be liable for failure to deliver on such dates.

c) Selection of the carrier and delivery route will be made by seller unless specifically designated by buyer.

d) Seller reserves the right to make deliveries in installments. Delay in delivery of one installment will not entitle buyer to cancel any other installment(s). Delivery of any installment of products within thirty (30) days after the date requested will constitute a timely delivery. Delivery of a quantity that varies from the quantity specified shall not relieve buyer of the obligation to accept delivery and pay for the products delivered.

e) Deliveries shall be made during normal business hours Monday through Friday. One attempt to deliver will be made. Should delivery need to be rescheduled, any additional costs incurred for redelivery and/or storage fees will be charged to the buyer. Seller shall use reasonable efforts to make timely delivery but shall be excused from any delays arising out of causes beyond its reasonable control. Any specific delivery dates that may be stated are approximate.

f) If completion of delivery is prevented through no fault of seller, seller may specify a reasonable alternative place of delivery. Buyer agrees that all costs of storage and transport incurred following an initial attempt at delivery are hereby allocated to and imposed upon buyer, and shall be added by seller to the sale price. Delivery may at any time be withheld by seller pending payment of any sum due from the buyer to seller. Seller will return Product via the incoming method unless an alternative method has been indicated on the purchase order or a change authorized by the buyer representative.

g) Deliveries made outside the 48 contiguous States may be subject to modified terms and conditions as stated within the order quote.

9. LIMITED WARRANTY

a) Products manufactured and/or branded by seller are warranted for a period of one year from time of delivery against defects in workmanship or materials or failure to operate as described in product data sheets under normal use. In some cases, the warranty period may exceed one year where a written warranty description specific to a certain product is stated in a contract or posted on a company website, product catalog or user's manual. Accessories and consumable goods such as batteries, chargers and accessory cables are warranted for four months.

b) Products manufactured by seller in accordance with buyer's instructions or specifications provided by seller are warranted for a period of one year from time of delivery against defects in workmanship or materials only under normal use. In some cases, the warranty period may exceed one year where a written warranty description specific to a certain product is stated in a contract or posted on a company website, product catalog or user's manual.

c) Calibration services are warranted for a period of one year from time of completion against defects in workmanship or materials or failure to operate as described in product data sheets under normal use.

d) The warranties set forth in this Section 9 shall not apply to any defect, failure, or damage arising from or in connection with: (i) improper use, or improper or inadequate maintenance and care; (ii) modifications to or repairs of the products performed by any party other than seller; (iii) combination of the products with any other technology, equipment, hardware, software, or other materials; (iv) use of the products in an environment not meeting the operating specifications for the products; (v) failure to properly transport, prepare, and store the products; (vi) acts of God; or (vii) any normal wear and tear or normal environmental degradation.

e) Products solely distributed by seller without alteration carry the warranty of the respective manufacturer only.

f) Seller will at seller's option and in seller's sole discretion, repair, replace or refund any products that are returned under warranty, and Seller's repair, replacement, or refunding of the price paid for a product under warranty shall be seller's sole liability, and buyer's sole remedy, for any breach of the warranties in this Section 9.

g) This warranty applies to the original purchaser only and is not transferable.

h) This warranty does not cover damage incurred during shipment which is the responsibility of the freight shipping company.

i) Buyer will bear the costs of access, de-installation, re-installation and transportation of the products to seller and back to buyer in connection with any warranty claims. Seller will reimburse the costs of transportation to seller and bear the costs of returning the repaired product or sending replacement product to buyer if the product is found to be covered under warranty.

j) Any repair or replacement pursuant to this limited warranty for products manufactured and/or branded by seller shall be warranted against the same defects re-occurring in a period of 12 months from time of delivery of the repaired or replaced product, or until the expiration of the original product warranty, which ever shall be the latter.

k) This limited warranty and remedies are expressly conditioned upon: (i) buyer's payment of the purchase price in full, (ii) buyer giving written notice of the defect, reasonably described, to seller within ten (10) days of the time when buyer discovers or ought to have discovered the defect, (iii) the storage, installation, operation, use, and maintenance of the products in compliance with product instructions, (iv) the existence of proper records of buyer's operation and maintenance of the products during the warranty period, (v) buyer providing seller with a reasonable opportunity to examine the products and the aforementioned records, and (vi) the absence of any unauthorized modification or repair of the products, including without limitation the removal or alternation of any serial numbers or product identifications.

l) THIS WARRANTY IS IN LIEU OF ANY AND ALL OTHER WARRANTIES, WHETHER ORAL, WRITTEN, EXPRESSED, IMPLIED OR STATUTORY. ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE AND NON-INFRINGEMENT ARE HEREBY DISCLAIMED.

10. RETURNS

a) Buyers wishing to return products must first obtain a Return Material Authorization (RMA) number from a Customer Service representative. Unauthorized returns will not be accepted at point of receipt. The RMA number must be printed on the outside of the package in order for it to be received and processed. Merchandise must be shipped prepaid.

b) Seller will determine in seller's sole discretion the appropriate remedies for returned items based on the product's limited warranty and circumstances of the return including a possible refund of purchase price, credit for future purchase, replacement, repair, return to buyer as-is, scrap with consent, and refund of shipping expenses.

c) Items stocked as finished goods and ordered in error must have a Return Material Authorization (RMA) number issued within 30 days of the original order. These parts are eligible for full credit only if the returned products and packaging are in mint and salable condition. A repackaging/restocking charge not to exceed 25% of the sale price may be charged on any products not returned unopened. Under no circumstances will credit be issued after 30 days from date of invoice or for orders exceeding $500.00 in total value. All freight charges are the responsibility of buyer.

d) Products not previously stocked as finished goods are not returnable unless found to be defective. These include cable assemblies, special orders, custom orders, orders for non-standard products, products requiring assembly or manufacturing activities prior to shipping (not stored in completed state).

e) Defective items must have a Return Material Authorization (RMA) number marked on the package prior to shipping.

f) After 30 days from invoice all merchandise returns for distributed products not manufactured by seller must be handled directly with that manufacturer in accordance with their warranty.

11. ORDER DISCREPANCIES

Claims for shortages, incorrect materials or invoicing errors must be made by buyer in writing within ten (10) business days after receipt of shipment. Claims for nonreceipt of shipment must be made in writing within ten (10) business days after receipt of invoice. No products shall be returned without seller's express instructions. Buyer must provide in writing the order number and describe all defects associated with the order.

12. LIMITATION OF LIABILITIES; INDEMNITY

a) IN NO EVENT WILL SELLER BE LIABLE TO BUYER OR TO ANY THIRD PARTY FOR ANY DELAY, FAILURE TO GIVE NOTICE OF DELAY, LOSS OF USE, SECURITY OR DATA BREACH, LOSS OF REVENUE OR PROFIT OR LOSS OF DATA, RECALL COSTS, SERVICE INTERRUPTIONS, DOWNTIME, TESTING, INSTALLATION, REPLACEMENT, OR REMOVAL COSTS, OR FOR ANY CONSEQUENTIAL, INCIDENTAL, INDIRECT, EXEMPLARY, SPECIAL OR PUNITIVE DAMAGES, WHETHER ARISING OUT OF BREACH OF CONTRACT, TORT (INCLUDING NEGLIGENCE), OR OTHERWISE, REGARDLESS OF WHETHER SUCH DAMAGE WAS FORESEEABLE AND WHETHER OR NOT SELLER HAS BEEN ADVISED OF

THE POSSIBILITY OF SUCH DAMAGES. SELLER'S AGGREGATE LIABILITY FOR ANY CLAIMS ARISING OUT OF OR IN CONNECTION WITH THIS AGREEMENT SHALL NOT EXCEED THE PURCHASE PRICE PAID BY BUYER FOR THE PRODUCTS WHICH ARE THE SUBJECT OF THE CLAIM. THE DISCLAIMERS AND LIMITATIONS IN THIS SECTION 12 WILL APPLY NOTWITHSTANDING ANY FAILURE OF ESSENTIAL PURPOSE OF ANY LIMITED REMEDY AND TO THE MAXIMUM EXTENT PERMITTED UNDER APPLICABLE LAW.

b) Buyer shall defend seller from and against any claims, actions, proceedings, or suits brought by any third party (i) alleging infringement of intellectual property rights arising out of or in connection with seller's compliance with buyer's drawings, specifications, requirements or instructions or (ii) arising out of or in connection with the products supplied by seller and incorporated into the buyer's products (each a "Claim") and shall indemnify and hold harmless seller from any costs, liabilities, damages, fines, judgments, or expenses (including reasonable attorneys' fees) arising out of or in connection with any Claim.

13. EXPORT COMPLIANCE

a) Items are controlled by the U.S. Government and authorized for export only to the country of ultimate destination for use by the ultimate consignee or end-user(s) identified in the invoice. They may not be resold, transferred, or otherwise disposed of, to any other country or to any person other than the authorized ultimate consignee or end-user(s), either in their original form or after being incorporated into other items, without first obtaining approval from the U.S. Government or as otherwise authorized by U.S. law and regulations. Buyer agrees to comply with all applicable export control laws, restrictions and regulations of the United States and those of the buyer's country, and shall not export, or transfer for the purpose of re-export, any product to any embargoed country or region, including but not limited to Cuba, the Crimean Region of Ukraine, Iran, North Korea, Sudan, and Syria, or to any denied, blocked, or designated person or entity as mentioned in any such United States or EU law or regulation. Buyer represents and warrants that it is not on the Denied Persons, Specially Designated Nationals or Debarred Persons List, as identified by the U.S. Treasury Office of Foreign Asset Control (OFAC) and by the U.S. Department of Commerce, Bureau of Industry and Security (BIS), or any other United States list of prohibited persons; is not owned or controlled by any person that is on one of those lists, or is otherwise prohibited by United States or other law from purchasing the products or services hereunder, and shall notify the seller immediately if buyer's status related to the above changes. Buyer shall be solely responsible to obtain any license to export, re-export or import as may be required. Buyer also agrees that it will not use these products in connection with the proliferation of weapons of mass destruction, including missiles, nuclear, chemical or biological weapons.

b) Seller shall not be liable for delays or refusals by governmental authorities or other authorities to grant licenses or approvals, nor for suspension or revocation thereof, nor for changes in export classification. Buyer must deliver requested information, including requested end-user information, necessary for export licenses to be granted, and or necessary for seller to determine if a license or other type of authorization is required.

c) For all custom orders, buyer shall provide seller with export classification information for all buyer property and information (including buyer drawings) delivered to seller in relation to this order. Export classification information includes the applicable export control classification, the country of origin and, for hardware only, the Harmonized Tariff Code. For such custom orders, seller will supply buyer with similar export classification information for products and/or information for which seller has design authority. Buyer and seller will promptly notify the other upon a change in classification information if any occurs prior to delivery.

14. GOVERNING LAW; VENUE

a) All matters arising out of or relating to this agreement, or a breach thereof, are governed by and construed in accordance with the internal laws of the State of California without giving effect to any choice or conflict of law provision or rule (whether of the State of California or any other jurisdiction) that would cause the application of the laws of any jurisdiction other than those of the State of California.

b) Any legal suit, action or proceeding arising out of or relating to this agreement, or a breach thereof, will be instituted in the federal or State courts located in the city of Irvine, California or its closest California venue. Each party irrevocably submits to the exclusive jurisdiction of the courts in any legal suit, action or proceeding.

15. LEGAL NOTICES

Any legal notice sent to seller from buyer, required or permitted hereunder, will be deemed to have been effectively delivered if in writing and served by personal delivery or sent by registered or certified mail with return receipt requested, postage prepaid, to seller at the primary address specified as seller's place of business.

16. INTELLECTUAL PROPERTY

a) Notwithstanding delivery of and the passing of title in any product, nothing in these terms and conditions shall have the effect of granting or transferring to, or vesting in, buyer any intellectual property rights in or to any products.

b) The drawings, text, product depictions, logos, content, product descriptions, and organization and taxonomy of seller's website, catalogue, product guides or other documents and media owned by the seller and of the described content there within are proprietary to the seller and protected by intellectual property laws, including but not limited to United States Copyright law and United States Trademark law. Whether seller owns copyrights in these works or not, their content and the selection, arrangement, coordination and structure of the arranged content there within are the sole property of the seller. Use of the above stated materials does not give anyone the right to modify, reproduce, transmit, publish, publicly display, adapt, or create derivative works or in any way exploit any of the materials without express written permission of the seller.

c) All trademarks referenced in seller's catalog or website or depicted within any seller's documents or digital media, whether registered in United States or other countries, may not be used without permission of the respective trademark owner. This applies to seller owned trademarks as well as those of seller's suppliers.

d) SELLER MAKES NO REPRESENTATION OR WARRANTY THAT THE PRODUCTS (OR BUYER'S USE OR EXPLOITATION THEREOF) WILL NOT INFRINGE ANY INTELLECTUAL PROPERTY RIGHTS.

17. SOFTWARE

a) To the extent that the product or services contain or are software, seller hereby grants to buyer a non-exclusive, non-transferable, personal license to use the software and related documentation. Buyer's use conclusively evidences its acceptance of this license. Title to the software shall at all times remain with seller. Buyer agrees that the software, all enhancements, related documentation, and derivative works are, and will remain the sole property of seller and includes valuable trade secrets. Buyer agrees to treat the software and related documentation as confidential and to not copy, reproduce, sub-license, or otherwise disclose the software and related documentation to third parties. Buyer agrees to not disassemble, decompile, reverse engineer, create derivative works from or otherwise translate, customize, localize, modify, add to, or in any way alter, rent, or loan the software or related documentation unless the operation is specifically authorized by law.

b) Third party product software Licenses are separate end user license agreements ("EULA") and not issued pursuant to the above stated personal license.

c) Buyer agrees to defend, indemnify and hold harmless seller from all damages and third party claims arising from unauthorized use or transfer of the software or firmware.

d) If the software is licensed for use in the performance of a U.S. Government prime contract or subcontract, buyer agrees that consistent with FAR 12.211 and 12.212, commercial computer software, computer software documentation and technical data for commercial items are licensed under seller's standard commercial license.

18. CONFIDENTIAL INFORMATION

Buyer agrees that all confidential information furnished by or obtained from seller in connection with the sale of items hereunder (including product data and manufacturing process data) shall be adequately safeguarded to prevent unauthorized disclosure. Buyer agrees not to (i) disclose any such information to any other person or entity, or (ii) use such information for any purpose, other than performing authorized activities directly related to the governing contract.

19. TOLERANCES

Unless otherwise agreed to in writing by seller, standard tolerances as described on seller's drawings, websites and/or posted catalog datasheets shall apply.

20. PRODUCT LINE CHANGES

Product specifications and availability are subject to change without notice. Seller reserves the right to change specifications or discontinue items at seller's sole discretion for any reason whatsoever including, but not limited to changing market conditions, product discontinuation, component unavailability, manufacturing cost changes and errors in advertisements.

21. FCC PART 15 AND PART 97 NOTICE

For systems operating within the jurisdiction of the United States Federal Communications Commission (FCC), buyer acknowledges that any amplification device it purchases is intended for use only in a transmission system certified under Part 15, Part 97 or other applicable section of the rules and regulations of the FCC, or that a legal exception to this requirement applies.

22. ASSIGNMENT

Buyer shall not assign this Agreement or any order hereunder without the prior written consent of the seller. Any assignment in violation of the foregoing will be void and of no force or effect. Seller may assign this Agreement or any order hereunder in seller's sole discretion and without restriction. This Agreement will be binding upon and inure to the benefit of the parties, their successors, and permitted assigns.

23. RELATIONSHIP

Nothing in in this Agreement or any product or service orders shall be construed to place the buyer or seller in the relationship of partners or joint ventures, and the buyer and seller shall have no power to obligate or bind the other in any manner whatsoever.

24. WAIVER

No waiver by seller of any breach of this Agreement by the buyer shall be considered as a waiver of the subsequent breach of the same or any other provision.

25. SEVERABILITY

If any provision or portion of this Agreement shall be adjudged invalid or unenforceable by a court of competent jurisdiction or by operation of any applicable law, that provision or portion of this Agreement shall be deemed omitted and the remaining provisions and portions shall remain in full force and effect.

26. LIENS AND TITLE

a) Buyer hereby grants to seller a security interest in any property owned by the buyer (including buyer's beneficial rights to property leased by seller) in the possession of seller or any of sellers' affiliates, at any time, to secure all amounts owed by buyer to seller under this Agreement.

b) In the case of repairs or overhauls performed pursuant to this Agreement, buyer grants seller a perfected security interest in all products retained in possession of seller upon which any repair or overhaul services have been performed by seller. Buyer further acknowledges and agrees that, in addition to the security interest and lien expressly granted by buyer to seller, seller shall have a lien on the product retained in possession of seller to the extent otherwise provided by law. Buyer acknowledges that the lien (whether granted by buyer or through the operation of law) for repairs or overhaul shall be for the full value of such work, and shall be superior to any lien or interest in favor of buyer, its parents, affiliates, or subsidiaries, or any other person who has knowledge of this Agreement. To the extent that seller maintains possession of product under repair, buyer agrees that seller is a secured creditor of buyer and has all the rights of a secured creditor.

c) With respect to products sold pursuant to this Agreement, buyer agrees and acknowledges that seller shall retain a security interest in such product, unless and until all payment for such products has been made and all other covenants and agreements of this Agreement have been performed in full. Accordingly, buyer agrees that it will not suffer or permit any lien or encumbrance to be established that effects the title to the product sold by seller pursuant hereto until seller has been paid in full. Buyer agrees that, in the event of buyer's insolvency, or in the event that any petition is filed by or against buyer under Chapter 7 or Chapter 11 of the Bankruptcy Code, seller may, at its discretion, recover all products sold pursuant to this Agreement and/or seek damages or costs under applicable laws.

27. STORAGE FEES

A storage fee will be applied monthly up to the maximum allowed by law on all repaired and overhauled units if delivery is not taken within five (5) days of notification.

28. FORCE MAJEURE

Notwithstanding anything else in this Agreement, no default, delay, or failure to perform on the part of seller will be considered a breach of this Agreement if such default, delay, or failure to perform is shown to be due to causes beyond reasonable control of seller, including, but not limited to, causes such as strikes, lockouts or other labor disputes, riots, civil disturbances, actions or inactions of governmental authorities or suppliers, epidemics, war, embargoes, severe weather, fire, earthquakes, acts of God or the public enemy, nuclear disasters, or default of a common carrier.

29. ENTIRE AGREEMENT; CONSTRUCTION; SURVIVAL

This Agreement sets forth the entire agreement and understanding of the Parties relating to the subject matter herein and supersedes all prior and contemporaneous communications, representations, discussions, and agreements between the Parties with respect to such subject matter. The titles and section headings used in this Agreement are for ease of reference only and shall not be used in the interpretation or construction of this Agreement. No rule of construction resolving any ambiguity in favor of the non-drafting party shall be applied hereto. The word "including", when used herein, is illustrative rather than exclusive and means "including, without limitation." In the event of any termination or expiration of this Agreement, buyer's obligations to pay amounts due hereunder and arising prior to the date of termination or expiration, as well as Sections 9, 12–18, and 21–29 shall survive such termination or expiration.

WARNING:

Products in this catalog can expose you to chemicals including phthalates, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information, go to www.P65Warnings.ca.gov. For specific products impacted, please visit www.pasternack.com.

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
CST-400	Web	
DBT-U	Web	
EZ-200-NMH-D	Web	
EZ-200-NMH-X	261	82
EZ-200-TFRP	Web	
EZ-200-TF-RP	289	48
EZ-200-TM	Web	
EZ-200-TM-RP	Web	
EZ-200-TM-X	286	21
EZ-240-4310M-X	242	74
EZ-240-NMH-D	Web	
EZ-240-NMH-X	261	83
EZ-240-QM-RA-X	266	91
EZ-240-SM-RA	Web	
EZ-240-SM-RA-X	270	40
EZ-240-SM-X	269	67
EZ-240-TF	Web	
EZ-240-TM	Web	
EZ-240-TM-X	286	22
EZ-400-716M-RA-X	244	38
EZ-400-716M-X	243	18
EZ-400-BM-X	247	45
EZ-400-FM-75	293	66
EZ-400-NF-BH	264	15
EZ-400-NM-75	Web	
EZ-400-NMC-2-D	260	59
EZ-400-NMH-75-X	295	12
EZ-400-NMH-PL-D	Web	
EZ-400-NMH-PL-X	261	84
EZ-400-NMH-RA-X	262	34
EZ-400-NMH-X	261	85
EZ-400-TM-X	286	23
EZ-400-UM	Web	
EZ-600-716M-X	243	19
EZ-600-NF	Web	
EZ-600-NF-BH	264	16
EZ-600-NF-X	263	77
EZ-600-NMC-2-D	260	60
EZ-600-NMH-RA-X	262	35
EZ-600-NMH-X	261	86
EZ-600-TM-X	286	24
EZ-600-UM	Web	
LMR-100A-FR	Web	
LMR-100A-PVC	226	18
LMR-100A-UF	Web	
LMR-195	226	19
LMR-195-FR	226	20
LMR-195-LLPL	226	21
LMR-195-UF	Web	
LMR-200	226	22
LMR-200-FR	226	23
LMR-200-UF	226	17
LMR-240	226	24
LMR-240-DB	226	25
LMR-240-FR	Web	
LMR-240-UF	226	26
LMR-400	226	27
LMR-400-75	226	1
LMR-400-DB	226	28
LMR-400-FR	Web	
LMR-400-LLPL	Web	
LMR-400-UF	227	29
LMR-500	227	30
LMR-500-DB	227	31
LMR-500-UF	Web	
LMR-600	227	32
LMR-600-DB	227	33
LMR-600-FR	Web	
LMR-600-UF	Web	
LMR-LW195	Web	
LMR-LW240	Web	
LMR-LW400	Web	
LMR-LW600	Web	
PE-020SR	229	89
PE-034SR	229	90
PE-047SR	229	91
PE-047SR-STRAIGHT	229	92
PE-1/2FAC	227	34
PE-1/2SFHC	227	35
PE-1/4SFHC	227	36
PE-118SR	229	93
PE-B150	226	2
PE-B159-BK	226	3
PE-B159-BL	226	4
PE-B159-GR	226	5
PE-B159-RD	226	6
PE-B159-WH	226	7
PE-B159-YW	226	8
PE-B305	226	9
PE-B400	227	37
PE-C100-LSZH	227	38
PE-C195	227	39
PE-C200	227	40
PE-C240	227	41
PE-C300	227	42
PE-C400	227	43
PE-C500	227	44
PE-C600	227	45
PE-P047	227	46
PE-P086	227	47
PE-P086HF	227	48
PE-P141	227	49
PE-P141HF	227	50
PE-P142LL	227	51
PE-P160LL	227	52
PE-P195	227	53
PE-P300LL	227	54
PE-S330	230	29
PE-SR047AL	229	94
PE-SR047AL-STRAIGHT	229	95
PE-SR047FL	229	96
PE-SR401AL-STRAIGHT	229	97
PE-SR401FL	229	98
PE-SR402-75	229	99
PE-SR402-75-STRAIGHT	229	1
PE-SR402AL	229	2
PE-SR402AL-STRAIGHT	229	3
PE-SR402FL	229	4
PE-SR402FLJ	229	5
PE-SR402TN	229	6
PE-SR402TN-STRAIGHT	229	7
PE-SR405AL	229	8
PE-SR405AL-STRAIGHT	229	9
PE-SR405FL	229	10
PE-SR405FLJ	229	11
PE-SR405TN	229	12
PE-SR405TN-STRAIGHT	229	13
PE-T1000	341	76
PE-T1003	341	84
PE-T1009	341	75
PE-T1010	341	85
PE-T1012	341	83
PE-T2000	342	5
PE-T2001	342	1
PE-T2003	342	92
PE-T2004	342	8
PE-T2006	342	89
PE-T2007	342	97
PE-T2010	342	14
PE-T2011	342	12
PE-T2012	342	13
PE-T2013	342	19
PE-T2014	342	11
PE-T2015	342	2
PE-T2016A	342	17
PE-T2017	342	16
PE-T2018	342	99
PE-T2023	342	18
PE-T2025	342	15
PE-W10AT002-30	388	8
PE-W10AT5001	377	30
PE-W10B001	369	33
PE-W10B002	369	34
PE-W10CA003	365	20
PE-W10CA004	365	21
PE-W10CP001-10	371	6
PE-W10CP001-20	371	4
PE-W10CP003-10	371	7
PE-W10CP003-20	371	5
PE-W10PS1001	382	65
PE-W10TR1001	385	82
PE-W10TS12001A	386	49
PE-W10TS15001	386	50
PE-W10TS19001	386	51
PE-W10TW1001	387	73
PE-W10TW1002	387	71
PE-W10TW1003	387	72
PE-W112B001	370	60
PE-W112B002	370	61
PE-W112S001-12	385	64
PE-W112S001-3	385	59
PE-W112S001-6	385	62
PE-W112S001-9	385	63
PE-W112SF005-12	380	85
PE-W112SF005-24	380	87
PE-W112SF005-36	380	89
PE-W112SF006-12	380	84
PE-W112SF006-24	380	86
PE-W112SF006-36	380	88
PE-W112TF005-12	381	25
PE-W112TF005-24	381	27
PE-W112TF005-36	381	29
PE-W112TF006-12	381	24
PE-W112TF006-24	381	26
PE-W112TF006-36	381	28
PE-W12AT002-30	388	9
PE-W12AT5001	377	31
PE-W12B001	369	35
PE-W12B002	369	36
PE-W12CA001	365	22
PE-W12CA002	365	23
PE-W12CP001-10	371	11
PE-W12CP001-20	371	9
PE-W12CP003-10	371	12
PE-W12CP003-20	371	10
PE-W12PS1001	382	66
PE-W12S001-12	384	3
PE-W12S001-9	384	1
PE-W12TR1001	385	83
PE-W12TS15001	386	52
PE-W12TW1001	387	77
PE-W12TW1002	387	74
PE-W12TW1003	387	75
PE-W13TB001	370	62
PE-W13TB002	370	63
PE-W13TB003A	370	64
PE-W13TB004	370	65
PE-W13TS001-12	385	73
PE-W13TS001-3	385	66
PE-W13TS001-6	385	70
PE-W13TS001-9	385	71
PE-W13TS002-12	385	74
PE-W13TS002A-6	385	65
PE-W13TS002-3	385	67
PE-W13TS002-9	385	72
PE-W13TSF005-12	380	91
PE-W13TSF005-24	380	93
PE-W13TSF005-36	380	95
PE-W13TSF006-12	380	90
PE-W13TSF006-24	380	92
PE-W13TSF006-36	380	94
PE-W13TTF005-12	381	31
PE-W13TTF005-24	381	33
PE-W13TTF005-36	381	34
PE-W13TTF006-12	381	30
PE-W13TTF006-24	381	32
PE-W13TTF006-36	381	35
PE-W13TR1001	386	38
PE-W159TR1001	386	40
PE-W159TR1002	386	39
PE-W15AT001-30	388	10
PE-W15AT5001	377	32
PE-W15B001	369	37
PE-W15B002	369	38
PE-W15CA001	365	24
PE-W15CA002	365	25
PE-W15CP001-10	371	15
PE-W15CP001-20	371	14
PE-W15CP003-10	371	16
PE-W15PS1001	382	67
PE-W15S001-12	384	7
PE-W15S001-3	384	4
PE-W15S001-6	384	5
PE-W15S001-9	384	6
PE-W15TS19001	386	53
PE-W15TS22001	386	54
PE-W15TW1001	387	80
PE-W15TW1002	387	78
PE-W15TW1003	387	79
PE-W187TR1001	386	42
PE-W187TR1002	386	41
PE-W19AT001-30	388	11
PE-W19AT5001	377	33
PE-W19B001	369	39
PE-W19B002	369	40
PE-W19CA001	365	26
PE-W19CA002	365	27
PE-W19CP001-10	371	20
PE-W19CP001-20	371	19
PE-W19CP003-10	371	17
PE-W19CP003-20	371	18
PE-W19PS1001	382	68
PE-W19S001-12	384	13
PE-W19S001-3	384	9
PE-W19S001-6	384	11
PE-W19S001-9	384	12
PE-W19TR1001	385	86
PE-W19TS22001	386	55
PE-W19TS28001	386	56
PE-W19TW1001	387	83
PE-W19TW1002	387	81
PE-W19TW1003	387	82
PE-W229TR1001	386	43
PE-W229TR1002	386	44
PE-W22AT001-30	388	12
PE-W22AT5001	377	34
PE-W22AT5002	377	35
PE-W22B001	369	41
PE-W22CA001	365	28
PE-W22CA002	365	29
PE-W22CP001-10	371	24
PE-W22CP003-20	371	22
PE-W22PS1001	382	69
PE-W22S001-12	384	19
PE-W22S001-3	384	15
PE-W22S001-6	384	16
PE-W22S001-9	384	18
PE-W22SF005-6	380	57
PE-W22SF005-12	380	58
PE-W22SF005-24	380	59
PE-W22TF005-6	380	96
PE-W22TF005-12	380	97
PE-W22TF005-24	380	98
PE-W22TR1002	385	87
PE-W22TS28001	386	57
PE-W22TS42001	386	58
PE-W22TW1001	387	87
PE-W22TW1002	387	84
PE-W22TW1003	387	85
PE-W284TR1001	386	45
PE-W28AT5001	377	36
PE-W28B001	369	44
PE-W28B002	369	45
PE-W28B003	369	46
PE-W28CA002	365	35
PE-W28CP002-10	372	28
PE-W28CP002-20	372	26
PE-W28CP003-10	372	27
PE-W28F001	369	22
PE-W28F002	369	23
PE-W28PS1002	382	70
PE-W28S001-3	384	21
PE-W28S001-9	384	24
PE-W28SF005-12	380	60
PE-W28SF005-24	380	61
PE-W28SF005-36	380	62
PE-W28TF005-12	380	99
PE-W28TF005-24	380	1
PE-W28TF005-36	380	2
PE-W28TR1002	385	92
PE-W28TR1003	385	91
PE-W28TR1004	385	94
PE-W28TR1005	385	95
PE-W28TS42001	386	59
PE-W28TS51001	386	60
PE-W28TW1001	387	91
PE-W28TW1002	387	89
PE-W28TW1003	387	90
PE-W34SF005-12	380	63
PE-W34SF005-24	380	64
PE-W34SF005-36	380	65
PE-W34TF005-12	380	3
PE-W34TF005-24	380	4
PE-W34TF005-36	380	5
PE-W34TR1001	385	98
PE-W42AT5001	377	37
PE-W42CA001	365	49
PE-W42CA002	365	50
PE-W42CP002-20	372	32
PE-W42CP004-10	372	34
PE-W42CP004-20	372	33
PE-W42F001	369	24
PE-W42F002	369	25
PE-W42F004	369	26
PE-W42PS1001	382	71
PE-W42S001-12	384	30
PE-W42S001A-6	384	28
PE-W42S001A-9	384	29
PE-W42S002-3	384	27
PE-W42SF005-12	380	66
PE-W42SF005-24	380	67
PE-W42SF005-36	380	68
PE-W42TF005-12	380	6
PE-W42TF005-24	380	7
PE-W42TF005-36	380	8
PE-W42TR1001	385	7
PE-W42TR1002	385	5
PE-W42TW1001	387	94
PE-W42TW1002	387	92
PE-W42TW1003	387	93
PE-W51B001	370	49
PE-W51S001-12	384	33
PE-W51S001-9	384	32
PE-W51SF005-12	380	69
PE-W51SF005-24	380	70
PE-W51SF005-36	380	71
PE-W51TF005-12	380	9
PE-W51TF005-24	381	10
PE-W51TF005-36	381	11
PE-W62B001	370	52
PE-W62B002	370	53
PE-W62B003	370	50
PE-W62B004	370	51
PE-W62S001-12	384	42
PE-W62S001-3	384	38
PE-W62S001-6	384	40
PE-W62S001-9	384	41
PE-W62S002-12	384	37
PE-W62S002-6	384	35
PE-W62S002-9	384	36
PE-W62SF005-12	380	72
PE-W62SF005-24	380	73
PE-W62SF005-36	380	74
PE-W62TF005-12	381	12
PE-W62TF005-24	381	13
PE-W62TF005-36	381	14
PE-W62TR1003	386	13
PE-W75B001	370	54
PE-W75B002	370	55
PE-W75S001A-6	384	43
PE-W75S001-3	384	44
PE-W75S001-6	384	46
PE-W75S001-9	384	47
PE-W75SF005-12	380	75
PE-W75SF005-24	380	76
PE-W75SF005-36	380	77
PE-W75TF005-12	381	15
PE-W75TF005-24	381	16
PE-W75TF005-36	381	17
PE-W90B001	370	56
PE-W90B002	370	57
PE-W90B003A	370	58
PE-W90B004A	370	59
PE-W90S001-12	384	57
PE-W90S001A-9	384	48
PE-W90S001-3	384	49
PE-W90S001-6	384	53
PE-W90S001-9	384	55
PE-W90S002-12	384	58
PE-W90S002-3	384	50
PE-W90S002-6	384	54
PE-W90S002-9	384	56
PE-W90SF005-12	380	78
PE-W90SF005-24	380	80
PE-W90SF005-36	380	82
PE-W90SF006-12	380	83
PE-W90SF006-24	380	79
PE-W90SF006-36	380	81
PE-W90TF005-12	381	19
PE-W90TF005-24	381	21
PE-W90TF005-36	381	23
PE-W90TF006-12	381	18
PE-W90TF006-24	381	20
PE-W90TF006-36	381	22
PE-W90TR1001	386	25
PE-W90TR1002	386	28
SC-100-TM-D	286	25
SPF-250	230	19
SPF-375	230	20
SPF-500	230	21
SPO-250	230	22
SPO-375	230	23
SPO-500	230	24
SPP-250-LLPL	230	25
SPP-375-LLPL	230	26
SPP-500-LLPL	230	27
TC-195-NMH-RA-D	262	36
TC-195-NMH-X	261	87
TC-195-SM-SS-X	269	68
TC-195-TM-X	286	26
TC-200-BM-X	247	46
TC-200-NMH-X	261	88
TC-200-SM-SS-X	269	69
TC-240-4310M-X	242	75
TC-240-BMC	247	27
TC-240-BM-X	247	47
TC-240-NF-BH-X	264	20
TC-240-NMC	260	62
TC-240-NMH-X	261	89
TC-240-SM-SS-X	269	71
TC-240-TM-X	286	27
TC-250-4310M-RA-LP	243	95
TC-250-716M-LP	244	30
TC-250-NM-LP	261	15
TC-250-NM-RA-LP	262	53
TC-375-4310M-LP	243	86
TC-375-716M-LP	244	31
TC-375-NM-LP	261	16
TC-400-4310M-X	242	76
TC-400-BM-X	247	48
TC-400-NF-X	263	78
TC-400-NMH-RA-D	262	47
TC-400-NMH-X	261	90
TC-400-SM-X	269	72
TC-400-TM-RA-D	286	52
TC-400-TM-X	286	28
TC-402-225F-LP	239	63
TC-402-225M-LP	239	60
TC-402-4195F-LP	242	70
TC-402-4310F-BH-LP	243	3
TC-402-4310F-LP	243	1
TC-402-4310M-LP	243	90
TC-402-4310M-RA-LP	243	96
TC-402-4310MS-LP	243	89
TC-402-716F-LP	245	65
TC-402-716F-PM-LP	245	75
TC-402-716M-LP	244	33
TC-402-716M-RA-LP	244	45
TC-402-NF-BH-LP	264	34
TC-402-NM-LP	261	17
TC-402-NM-RA-LP	262	56
TC-402-NX10M-LP	266	75
TC-402-NX10M-RA-LP	266	77
TC-402-QM-LP	266	90
TC-402-QM-RA-LP	266	1
TC-402-SM-LP	270	8
TC-500-4310M-LP	243	88
TC-500-716M-LP	244	32
TC-500-NM-LP	261	13
TC-600-4310M-X	242	77
TC-600-NMH-X	261	91
TC-SPO500-NM-RA-LP	262	54
TC-SPP250-4195M-RALP	242	67
TC-SPP250-4310F-LP	243	99
TC-SPP250-716F-LP	244	63
TC-SPP250-716M-RA-LP	244	44
TC-SPP250-NF-BH-LP	264	33
TC-SPP375-716F-LP	245	64
TC-SPP375-NF-LP	263	28
TFT-402-LF	230	28
PE1001	Web	
PE1002	Web	
PE1003	Web	
PE1004-1-100PK	Web	
PE1004-2-100PK	Web	
PE1004-3-100PK	Web	
PE1005-2-100PK	Web	
PE1005-3-100PK	Web	
PE1006-1-100PK	Web	
PE1006-2-100PK	Web	
PE1007-100PK	Web	
PE1008-100PK	Web	
PE1009-100PK	Web	
PE1010	Web	
PE1013	Web	
PE1015	Web	
PE1016	Web	
PE1017	Web	
PE1527	Web	
PE1607	Web	
PE1400	322	62
PE1401	322	61
PE1402	322	63
PE1406	322	64
PE1513	53	13
PE1514	53	11
PE1516	53	18
PE1517	53	15
PE1518	53	16
PE1519	53	22
PE1520	53	23
PE1521	53	24
PE1522	53	26
PE1523	53	29
PE1524	53	25
PE1525	53	19
PE1528	53	12
PE1603	87	46
PE1604	87	40
PE1605	87	43
PE1608	87	32
PE1610	87	29
PE1611	87	33
PE1612	87	35
PE1613	87	34
PE1614	87	36
PE1615	87	37
PE1616	87	38
PE1617	87	41
PE1618	87	42
PE1619	87	27
PE1620	87	28
PE1621	87	39
PE1622	87	45
PE11S1001	Web	
PE11S1002	336	1
PE11S3900	336	3
PE11S3901	336	2
PE11S3902	336	4
PE11S3903	336	5
PE11S3904	336	6
PE11S3905	336	7
PE12D1000	371	96
PE12D1001	371	95
PE12D1002	371	94
PE12D1003	Web	
PE12D1004	371	93
PE12D1005	371	92
PE13U1000	371	3
PE13U1001	371	2
PE13U1002	371	1
PE13U1003	371	99
PE13U1004	371	98
PE13U1005	371	97
PE15A1000	54	74
PE15A1001	54	83
PE15A1002	55	89
PE15A1003	55	98
PE15A1003M	55	97
PE15A1004	55	1
PE15A1005	54	80
PE15A1006	55	88
PE15A1007	54	41
PE15A1008	54	62
PE15A1009	54	58
PE15A1010	54	85
PE15A1011	54	52
PE15A1012	54	54
PE15A1013	54	55
PE15A1014	54	66
PE15A1017	54	70
PE15A1018	54	71
PE15A1019	54	75
PE15A1023	54	78
PE15A1024	54	79
PE15A1025	55	99
PE15A1026	55	96
PE15A1027	55	95
PE15A1028	54	81
PE15A1030	54	86
PE15A1031	54	77
PE15A1032	55	91
PE15A1033	55	94
PE15A1034	54	82
PE15A1035	54	87
PE15A1039	55	12
PE15A1040	55	13
PE15A1041	54	84
PE15A1042	54	68
PE15A1043	54	47
PE15A1044	54	48
PE15A1045	54	46
PE15A1046	54	42
PE15A1047	54	45
PE15A1048	54	50
PE15A1049	54	53
PE15A1050	54	65
PE15A1051	54	59
PE15A1052	54	56
PE15A1053	54	67
PE15A1054	54	57
PE15A1055	54	43
PE15A1057	54	61
PE15A1059	54	44
PE15A1060	54	64
PE15A1061	54	63
PE15A1063	54	49
PE15A1064	54	60
PE15A1065	54	51
PE15A1066	54	69
PE15A1067	54	73
PE15A1068	54	72
PE15A1070	54	76
PE15A1071	55	93
PE15A1072	55	92
PE15A1073	55	19
PE15A1074	55	11
PE15A1075	55	10
PE15A1076	382	51
PE15A1077	382	52
PE15A2001	54	39
PE15A2003	54	38
PE15A2004	54	40
PE15A3001	51	13
PE15A3004	51	12
PE15A3005	51	20
PE15A3007	51	11
PE15A3008	51	21
PE15A3009	51	37
PE15A3014	51	16
PE15A3015	51	17
PE15A3016	51	31
PE15A3017	51	46
PE15A3018	51	44
PE15A3019	51	45
PE15A3020	51	47
PE15A3021	51	14
PE15A3022	51	34
PE15A3023	51	10
PE15A3024	51	49
PE15A3025	51	51
PE15A3036	51	8
PE15A3037	52	98
PE15A3038	51	38
PE15A3253	52	68
PE15A3254	52	63
PE15A3255	52	65
PE15A3256	52	66
PE15A3257	52	73
PE15A3258	52	74
PE15A3259	52	82
PE15A3260	52	87
PE15A3261	52	91
PE15A3262	51	24
PE15A3263	51	22
PE15A3264	51	23
PE15A3265	51	33
PE15A3266	52	92
PE15A3267	52	67
PE15A3268	52	88
PE15A3269	52	61
PE15A3270	52	76
PE15A3271	52	75
PE15A3272	52	62
PE15A3273	52	83
PE15A3274	52	85
PE15A3275	52	95
PE15A3276	52	69
PE15A3290	52	70
PE15A3291	52	71
PE15A3292	52	77
PE15A3293	52	78
PE15A3294	52	80
PE15A3295	52	79
PE15A3296	52	84
PE15A3300	55	2
PE15A3301	52	72
PE15A3302	52	81
PE15A3303	52	86
PE15A3304	52	89
PE15A3305	52	90
PE15A3306	52	93
PE15A3307	52	94
PE15A3308	52	57
PE15A3309	52	60
PE15A3310	52	59
PE15A3311	52	58
PE15A3312	52	64
PE15A3500	53	1
PE15A3503	52	53
PE15A3505	52	55
PE15A3506	52	54
PE15A3507	52	56
PE15A3508	53	7
PE15A3509	53	8
PE15A3510	53	9
PE15A3511	53	10
PE15A3512	53	2
PE15A3513	53	3
PE15A3514	53	4
PE15A3515	53	5
PE15A3595	53	6
PE15A3900	52	96
PE15A3901	52	97
PE15A4001	51	42
PE15A4002	51	48
PE15A4003	51	27
PE15A4004	51	43
PE15A4005	51	28
PE15A4006	57	79
PE15A4007	57	80
PE15A4008	57	76
PE15A4009	56	29
PE15A4011	56	48
PE15A4012	56	60
PE15A4013	56	71
PE15A4014	56	72
PE15A4015	56	73
PE15A4016	56	44
PE15A4017	55	27
PE15A4018	56	28
PE15A4019	56	30
PE15A4020	58	38
PE15A4021	57	84
PE15A4022	51	52
PE15A4023	383	79
PE15A4024	383	80
PE15A4025	56	43
PE15A4026	56	42
PE15A4027	51	35
PE15A4028	51	50
PE15A4029	51	9
PE15A4030	51	36
PE15A4031	Web	
PE15A4032	51	7
PE15A4037	51	19
PE15A4038	51	15
PE15A4039	51	18
PE15A4040	51	25
PE15A4041	51	26
PE15A4042	51	29
PE15A4043	51	30
PE15A4044	51	40
PE15A4045	51	41
PE15A4046	51	39
PE15A4050	57	89
PE15A4051	51	32
PE15A4052	56	31
PE15A4052F	56	32
PE15A4053	56	35
PE15A4053F	56	36
PE15A4054	56	49
PE15A4054F	56	50
PE15A4055	56	51
PE15A4055F	56	52
PE15A4056	56	53
PE15A4056F	56	54
PE15A4057	56	55
PE15A4057F	56	56
PE15A4058	56	57
PE15A4058F	56	58
PE15A4060	56	63
PE15A4060F	56	64
PE15A4061	56	66
PE15A4061F	56	65
PE15A4062	56	69
PE15A4062F	56	70
PE15A4063	57	78
PE15A4063F	57	77
PE15A4064	57	82
PE15A4064F	57	83
PE15A4065	57	87
PE15A4065F	57	88
PE15A4067	57	90
PE15A4067F	57	91
PE15A4069	57	92
PE15A4069F	57	93
PE15A4072	55	25
PE15A5001	58	15
PE15A5002	56	59
PE15A5003	58	26
PE15A5004	57	2
PE15A5005	58	16
PE15A5006	58	24
PE15A5007	58	25
PE15A5008	58	27
PE15A5009	58	28
PE15A5010	Web	
PE15A5011	58	39
PE15A5013	Web	
PE15A5015	58	18
PE15A5016	59	59
PE15A5017	58	47
PE15A5018	58	23
PE15A5020	57	6
PE15A5021	57	81
PE15A5024	59	54
PE15A5025	59	55
PE15A5026	58	50
PE15A5027	58

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE1V11011	338	59
PE1V11012	338	60
PE1V11013	338	61
PE1V11014	338	62
PE1V11015	338	63
PE1V11016	338	64
PE1V11017	338	65
PE1V11018	338	66
PE1V11019	338	67
PE1V11020	338	68
PE1V11021	338	69
PE1V11022	338	70
PE1V11023	338	71
PE1V11024	338	72
PE1V11025	338	73
PE1V11026	338	74
PE1V11027	338	75
PE1V12000	339	89
PE1V12001	339	90
PE1V12002	339	91
PE1V12003	339	92
PE1V12004	339	93
PE1V12005	339	94
PE1V12006	339	95
PE1V12007	339	96
PE1V12008	339	97
PE1V13000	339	98
PE1V13001	339	99
PE1V13002	339	1
PE1V13003	339	2
PE1V13004	339	3
PE1V13005	339	4
PE1V13006	339	5
PE1V13007	339	6
PE1V13008	339	7
PE1V13009	339	8
PE1V13010	339	9
PE1V13011	339	10
PE1V13012	339	11
PE1V13013	339	12
PE1V13014	339	13
PE1V13015	339	14
PE1V14000	338	76
PE1V14001	338	77
PE1V14002	338	78
PE1V14003	338	79
PE1V14004	338	80
PE1V14005	338	81
PE1V14006	338	82
PE1V14007	338	83
PE1V14008	338	84
PE1V14009	338	85
PE1V14010	338	86
PE1V15000	338	87
PE1V15001	338	88
PE1V21000	337	8
PE1V21001	337	10
PE1V21002	337	12
PE1V21003	337	14
PE1V21004	337	16
PE1V21005	337	18
PE1V21006	337	20
PE1V21007	337	22
PE1V21008	337	24
PE1V21009	337	26
PE1V21010	337	28
PE1V21011	337	30
PE1V21012	337	32
PE1V21013	337	34
PE1V21014	337	36
PE1V21015	337	38
PE1V21016	337	40
PE1V21017	337	42
PE1V21018	337	44
PE1V21019	337	46
PE1V31000	339	15
PE1V31001	339	16
PE1V31002	339	17
PE1V31003	339	18
PE1V31004	339	19
PE1V31005	339	20
PE1V31006	Web	
PE1V31007	339	21
PE1V31008	Web	
PE1V31009	339	22
PE1V31010	339	23
PE1V31011	340	24
PE1V31012	Web	
PE1V31013	Web	
PE1V31015	340	25
PE1V31016	340	26
PE1V31017	340	35
PE1V31018	340	27
PE1V31019	340	28
PE1V31020	340	36
PE1V31021	340	33
PE1V31022	340	34
PE1V31023	340	29
PE1V31024	340	37
PE1V31025	340	30
PE1V31026	340	31
PE1V31027	340	32
PE1V31028	340	38
PE1V31029	340	39
PE1V34000	340	40
PE1V34001	340	41
PE1V34002	Web	
PE1V34003	340	42
PE2000	319	36
PE2001	320	61
PE2002	Web	
PE2003	320	88
PE2004	320	62
PE2005	320	77
PE2006	320	73
PE2007	Web	
PE2008	320	89
PE2009	321	20
PE2011	320	98
PE2012	321	26
PE2014	320	3
PE2015	Web	
PE2017	Web	
PE2018	Web	
PE2020	321	9
PE2021	321	32
PE2023	321	12
PE2024	Web	
PE2026	320	4
PE2027	321	10
PE2028	319	51
PE2029	321	28
PE2030	Web	
PE2031	321	27
PE2032	319	41
PE2033	320	97
PE2034	320	2
PE2035	321	6
PE2036	319	53
PE2037	319	57
PE2038	320	63
PE2039	320	67
PE2040	320	69
PE2041	321	30
PE2042	Web	
PE2044	319	37
PE2045	Web	
PE2046	Web	
PE2047	319	39
PE2048	321	40
PE2049	321	42
PE2050	306	46
PE2051	Web	
PE2052	306	52
PE2053	Web	
PE2054	Web	
PE2055	307	59
PE2056	Web	
PE2056A	307	62
PE2057	307	63
PE2058	306	53
PE2059	306	56
PE2061	321	43
PE2062	321	41
PE2063	320	79
PE2064	320	81
PE2065	320	86
PE2066	320	82
PE2067	320	80
PE2068	320	84
PE2069	Web	
PE2070	319	38
PE2071	Web	
PE2072	Web	
PE2073	Web	
PE2074	320	96
PE2076	Web	
PE2077	319	55
PE2078	319	54
PE2079	Web	
PE2079A	319	56
PE2080	321	7
PE2081	319	52
PE2082	320	78
PE2083	320	85
PE2084	320	83
PE2085	Web	
PE2086	Web	
PE2087	Web	
PE2088	320	94
PE2089	321	23
PE2090	321	17
PE2091	321	36
PE2092	320	93
PE2093	321	16
PE2094	321	22
PE2095	321	35
PE2096	Web	
PE2200-10	303	39
PE2200-20	303	39
PE2200-30	303	39
PE2201-10	304	56
PE2201-30	304	58
PE2202-6	304	65
PE2202-30	304	65
PE2203-10	304	78
PE2203-20	304	80
PE2203-30	304	80
PE2204-6	304	81
PE2204-10	304	81
PE2204-20	304	81
PE2204-30	304	81
PE2205-20	304	90
PE2205-30	304	90
PE2206-6	304	93
PE2207-6	304	95
PE2207-10	304	95
PE2207-30	304	97
PE2208-6	303	41
PE2208-10	303	43
PE2208-20	303	45
PE2209-6	304	60
PE2209-20	304	64
PE2210-6	304	67
PE2210-10	304	69
PE2210-20	304	71
PE2211-6	304	82
PE2211-10	304	82
PE2211-20	304	82
PE2213-10	304	50
PE2215-6	304	72
PE2215-10	304	75
PE2215-20	304	77
PE2217-10	305	20
PE2217-20	305	21
PE2217-30	305	22
PE2218-10	305	24
PE2218-20	305	25
PE2218-30	305	26
PE2219-20	305	27
PE2220-10	305	30
PE2220-20	305	31
PE2220-30	305	32
PE2221-10	305	33
PE2222-30	305	34
PE2223-10	305	35
PE2223-20	305	36
PE2223-30	305	37
PE2224-20	305	38
PE2226-30	303	32
PE2230-30	303	36
PE2235-30	303	37
PE2236-35	303	35
PE2239-30	303	34
PE2240-30	303	25
PE2242-10	303	46
PE2242-20	303	46
PE2242-30	303	48
PE2243-10	303	49
PE2243-16	303	49
PE2243-20	303	49
PE2243-30	303	49
PE20DV000	319	49
PE20DV001	319	60
PE20DV002	320	71
PE20DV003	320	74
PE20DV004	320	76
PE20DV005	319	50
PE20DV006	320	72
PE20DV007	319	44
PE20DV008	319	45
PE20DV009	319	43
PE20DV010	320	65
PE20DV011	320	75
PE20DV012	320	66
PE20DV013	319	47
PE20DV014	319	46
PE20DV015	320	68
PE20DV016	319	48
PE20DV017	319	59
PE20DV018	320	70
PE20DV019	319	42
PE20DV020	320	64
PE20DV1026	341	77
PE20DV1027	341	78
PE20DV1028	341	79
PE20DV1029	341	80
PE20DV1030	341	81
PE20DV1031	341	82
PE20DV1032	Web	
PE20DV1032A	320	92
PE20DV1033	Web	
PE20DV1033A	320	91
PE20DV1034	Web	
PE20DV1034A	321	18
PE20DV1035	Web	
PE20DV1035A	Web	
PE20DV1036	Web	
PE20DV1036A	321	24
PE20DV1037	Web	
PE20DV1038	Web	
PE20DV1038A	321	38
PE20DV1039	Web	
PE20DV1039A	321	37
PE20DV1040	319	58
PE20DV1041	319	40
PE20DV1044	319	27
PE20DV1045	319	28
PE20DV1046	319	32
PE20DV1047	319	33
PE20DV1048	319	34
PE20DV1049	319	26
PE20DV1050	319	30
PE20DV1051	319	31
PE20DV1052	319	35
PE20DV1053	319	25
PE20DV1056	320	87
PE20DV1057	319	24
PE20DV1058	320	99
PE20DV1059	320	1
PE20DV1060	320	8
PE20DV1061	321	8
PE20DV1062	321	11
PE20DV1063	321	13
PE20DV1064	321	14
PE20DV1065	321	15
PE20DV1067	321	29
PE20DV1068	321	31
PE20DV1069	321	33
PE20DV1073	319	29
PE20S0001	322	45
PE20S0002	322	47
PE20S0003	322	46
PE20S0004	322	44
PE20S0005	322	49
PE20S0006	322	48
PE20S0007	322	50
PE20S0008	322	56
PE20S0009	322	54
PE20S0010	322	52
PE20S0011	322	51
PE20S0012	322	53
PE20S0013	322	55
PE20S0014	322	57
PE20S0015	322	58
PE20S0016	322	60
PE20S0017	322	59
PE20S0019	321	19
PE20S0020	321	25
PE20S0021	321	39
PE20S0022	320	90
PE20S0023	321	34
PE20S0024	321	21
PE20S0025	320	95
PE2228A-30	303	33
PE2242A-20	303	47
PE2BL1000	86	24
PE2BL1001	86	20
PE2BL1002	86	21
PE2BL1003	86	22
PE2BL1004	86	23
PE2BL1005	86	25
PE2BL1006	86	26
PE2CP000-10	304	73
PE2CP000-20	304	76
PE2CP000-30	304	76
PE2CP001-10	304	86
PE2CP001-20	304	86
PE2CP002-6	304	51
PE2CP002-10	304	51
PE2CP002-20	304	51
PE2CP003-6	303	40
PE2CP003-10	303	42
PE2CP003-20	303	44
PE2CP004-6	304	66
PE2CP004-10	304	68
PE2CP004-20	304	70
PE2CP005-6	304	59
PE2CP005-10	304	61
PE2CP005-20	304	63
PE2CP011	306	44
PE2CP013	306	48
PE2CP017	306	51
PE2CP019	306	55
PE2CP021	306	47
PE2CP023	306	54
PE2CP025-10	304	52
PE2CP1000	305	99
PE2CP1001	305	17
PE2CP1002	305	1
PE2CP1003	305	2
PE2CP1004	305	18
PE2CP1005	305	3
PE2CP1006	305	15
PE2CP1007	305	4
PE2CP1008	305	5
PE2CP1009	305	19
PE2CP1010	305	7
PE2CP1011	305	9
PE2CP1012	305	10
PE2CP1013	305	11
PE2CP1014	305	23
PE2CP1015	305	12
PE2CP1016	305	13
PE2CP1017	305	16
PE2CP1018	305	28
PE2CP1019	305	14
PE2CP1020	305	8
PE2CP1021	305	6
PE2CP1022	307	61
PE2CP1023-6	303	31
PE2CP1023-10	303	31
PE2CP1023-20	303	31
PE2CP1023-30	303	31
PE2CP1024-6	304	53
PE2CP1024-30	304	55
PE2CP1025-10	304	54
PE2CP1025-20	304	54
PE2CP1026	306	64
PE2CP1027	306	65
PE2CP1028	306	66
PE2CP1029	306	67
PE2CP1032	306	68
PE2CP1033	306	69
PE2CP1034	306	70
PE2CP1035	306	71
PE2CP1036	306	72
PE2CP1037	306	73
PE2CP1038	306	74
PE2CP1039	306	75
PE2CP1040	306	76
PE2CP1041	306	77
PE2CP1042	306	78
PE2CP1043	306	79
PE2CP1044	306	80
PE2CP1045	306	81
PE2CP1046	306	82
PE2CP1047	306	83
PE2CP1048	306	84
PE2CP1049	306	85
PE2CP1050	306	86
PE2CP1051	306	87
PE2CP1052	306	88
PE2CP1053	306	89
PE2CP1054	306	90
PE2CP1055	306	91
PE2CP1056	306	92
PE2CP1057	303	26
PE2CP1058	303	20
PE2CP1059	302	10
PE2CP1060	302	16
PE2CP1061	303	27
PE2CP1062	303	21
PE2CP1063	302	11
PE2CP1064	302	17
PE2CP1065	303	28
PE2CP1066	303	22
PE2CP1067	302	12
PE2CP1068	303	18
PE2CP1069	303	29
PE2CP1070	303	23
PE2CP1071	302	13
PE2CP1072	303	19
PE2CP1073	303	30
PE2CP1074	303	24
PE2CP1075	302	14
PE2CP1076	302	15
PE2CP1100	304	83
PE2CP1101	304	88
PE2CP1102	304	62
PE2CP1103	304	74
PE2CP1104	304	84
PE2CP1105	304	89
PE2CP1106	304	92
PE2CP1107	304	94
PE2CP1108	304	57
PE2CP1109	304	79
PE2CP1110	304	85
PE2CP1111	304	96
PE2CP1112	304	91
PE2CP1113	305	29
PE2CP1114-10	303	38
PE2CP1114-20	303	38
PE2CP1120-10	304	87
PE2CP1120-30	304	87
PE2CP1120-20	304	87
PE2CP1121-30	304	98
PE2CP1122-10	302	4
PE2CP1122-20	302	4
PE2CP1122-30	302	4
PE2CP1124-10	302	7
PE2CP1124-20	302	7
PE2CP1125-10	302	8
PE2CP1125-20	302	8
PE2CP1125-30	302	8
PE2CP1125-15	302	8
PE2CP1126-6	302	9
PE2CP1126-10	302	9
PE2CP1126-20	302	9
PE2CP1127-10	302	1
PE2CP1127-20	302	1
PE2CP1129-10	302	6
PE2CP1133-10	302	5
PE2CP1133-20	302	5
PE2CP1133-30	302	5
PE2CP1134-10	302	2
PE2CP1135-20	302	3
PE2CP1140	306	45
PE2CP1141	306	58
PE2CP1142	307	60
PE2CP1143	306	57
PE2CP1144	306	49
PE2CP1145	306	50
PE2CP1146	306	42
PE2CP1147	306	40
PE2CP1148	306	43
PE2CP1149	306	41
PE2CP1150	306	39
PE2CP1151	307	94
PE2CP1152	307	95
PE2CP1153	307	96
PE2CP1154	307	97
PE2CP1155	307	98
PE2CP1157	307	99
PE2CP1158	307	1
PE2CP1159	307	2
PE2CP1160	307	3
PE2CP1161	307	93
PE2PB1000	349	31
PE2PB1001	349	33
PE2PB1002	349	27
PE2PB1003	349	29
PE2PB1004	349	30
PE2PB1005	349	32
PE2PB1006	349	26
PE2PB1007	349	28
PE2V000	337	9
PE2V001	337	11
PE2V002	337	13
PE2V003	337	15
PE2V004	337	17
PE2V005	337	19
PE2V006	337	21
PE2V007	337	23
PE2V008	337	25
PE2V009	337	27
PE2V010	337	29
PE2V011	337	31
PE2V012	337	33
PE2V013	337	35
PE2V014	337	37
PE2V015	337	39
PE2V016	337	41
PE2V017	337	43
PE2V018	337	45
PE2V019	337	47
PE300	168	85
PE302	138	68
PE304	164	62
PE310-KIT	349	19
PE312	166	49
PE315	101	90
PE317	101	96
PE319	100	72
PE330	137	40
PE331	141	52
PE332	146	3
PE333	167	55
PE334	206	41
PE335	148	47
PE336	167	56
PE337	146	4
PE338	176	43
PE340	171	80
PE341	167	58
PE342	182	13
PE343	137	18
PE344	142	90
PE345	139	90
PE346	208	95
PE347	206	42
PE348	211	73
PE349	148	45
PE350	168	86
PE351	169	24
PE352	138	69
PE354	146	7
PE356	189	93
PE360	100	66
PE361	101	82
PE363	99	53
PE364	100	58
PE366	167	54
PE367	169	28
PE369	101	89
PE3000	Web	
PE3002	Web	
PE3003	170	50
PE3005	Web	
PE3006	Web	
PE3009	Web	
PE3010	Web	
PE3012	Web	
PE3013	165	1
PE3015	213	4
PE3016	Web	
PE3020	121	77
PE3023	205	9
PE3025	124	47
PE3027	Web	
PE3028	Web	
PE3030	Web	
PE3031	Web	
PE3034	142	4
PE3038	129	12
PE3041	221	73
PE3042	144	59
PE3044	124	48
PE3047	122	95
PE3049	Web	
PE3050	185	82
PE3051	172	39
PE3052	124	68
PE3056	171	98
PE3057	212	88
PE3058	175	17
PE3061	123	24
PE3062	138	57
PE3066	Web	
PE3067	120	43
PE3069	Web	
PE3070	Web	
PE3071	140	25
PE3074	208	84
PE3075	121	67
PE3076	164	82
PE3078	171	95
PE3080	149	70
PE3081	121	70
PE3082	121	78
PE3083	129	11
PE3085	132	81
PE3087	120	52
PE3088	124	69
PE3089	177	79
PE3093	172	21
PE3094	125	72
PE3095	129	13
PE3097	145	64
PE3098	131	63
PE3100	221	74
PE3102	171	9
PE3103	122	19
PE3104	158	98
PE3107	Web	
PE3108	132	90
PE3109	190	24
PE3112	221	75
PE3116	121	86
PE3117	159	18
PE3120	125	92
PE3121	167	78
PE3122	202	46
PE3125	Web	
PE3126	Web	
PE3128	Web	
PE3130	197	98
PE3133	145	75
PE3134	203	49
PE3137	170	71
PE3138	168	87
PE3139	202	47
PE3141	184	62
PE3143	140	19
PE3145	129	1
PE3146	Web	
PE3147	184	51
PE3148	Web	
PE3149	185	80
PE3152	185	81
PE3154	176	50
PE3156	185	78
PE3157	203	50
PE3158	129	5
PE3160	171	6
PE3166	196	75
PE3168	140	26
PE3170	145	76
PE3171	171	3
PE3172	174	80
PE3174	177	59
PE3176	177	57
PE3178	176	53
PE3179	182	11
PE3181	174	81
PE3182	129	2
PE3183	109	74
PE3184	172	37
PE3185	109	77
PE3187	174	87
PE3188	172	13
PE3189	109	75
PE3190	129	6
PE3192	109	80
PE3193	165	8
PE3194	210	41
PE3195	Web	
PE3197	Web	
PE3199	109	76
PE3200	129	4
PE3202	Web	
PE3205	109	82
PE3207	144	40
PE3209	Web	
PE3210	174	97
PE3211	129	3
PE3216	144	41
PE3217	143	8
PE3218	144	43
PE3221	160	39
PE3223	195	56
PE3224	160	40
PE3226	175	5
PE3227	143	14
PE3228	Web	
PE3230	170	63
PE3231	212	95
PE3232	141	61
PE3233	160	42
PE3234	146	6
PE3236	196	62
PE3237	Web	
PE3238	198	37
PE3242	195	57
PE3244	198	34
PE3245	168	4
PE3251	Web	
PE3252	144	58
PE3253	172	14
PE3254	145	67
PE3255	140	30
PE3258	132	94
PE3259	184	52
PE3263	132	95
PE3264	120	42
PE3265	132	96
PE3267	Web	
PE3268	151	28
PE3269	132	97
PE3271	162	23
PE3272	150	23
PE3273	162	21
PE3274	Web	
PE3275	162	22
PE3277	Web	
PE3278	162	24
PE3280	145	80
PE3281	Web	
PE3282	145	78
PE3285	145	79
PE3286	Web	
PE3287	Web	
PE3288	145	82
PE3290	130	41
PE3291	163	54
PE3293	130	42
PE3295	130	40
PE3297	130	43
PE3299	131	54
PE3301	131	55
PE3302	164	60
PE3304	131	53
PE3306	131	56
PE3307	220	62
PE3309	130	46
PE3311	130	47
PE3312	Web	
PE3314	130	45
PE3316	130	48
PE3318	164	63
PE3319	169	40
PE3320	142	3
PE3321	163	55
PE3323	163	52
PE3325	121	82
PE3326	Web	
PE3327	121	76
PE3328	Web	
PE3329	Web	
PE3333	171	8
PE3334	158	1
PE3335	Web	
PE3338	159	23
PE3340	129	18
PE3341	219	50
PE3343	125	90
PE3344	170	49
PE3345	165	2
PE3347	183	41
PE3348	158	4
PE3349	195	58
PE3351	124	50
PE3352	170	74
PE3353	167	72
PE3355	121	81
PE3357	129	16
PE3358	121	85
PE3360	121	94
PE3361	167	75
PE3362	221	79
PE3364	125	74
PE3365	132	78
PE3366	124	61
PE3367	165	20
PE3368	122	7
PE3369	167	68
PE3370	124	53
PE3371	122	1
PE3372	Web	
PE3373	124	49
PE3374	Web	
PE3375	122	5
PE3376	221	80
PE3377	167	79
PE3378	124	46
PE3380	184	59
PE3381	124	51
PE3382	173	52
PE3383	Web	
PE3384	124	52
PE3385	167	71
PE3386	Web	
PE3387	168	8
PE3388	221	81
PE3389	124	56
PE3390	Web	
PE3391	Web	
PE3393	170	64
PE3394	207	52
PE3395	158	2
PE3396	220	51
PE3398	220	53
PE3400	220	54
PE3402	207	70
PE3405	171	10
PE3407	151	45
PE3408	207	72
PE3409	158	3
PE3411	170	73
PE3412	151	29
PE3414	207	58
PE3416	158	6
PE3417	183	30
PE3418	207	50
PE3420	169	42
PE3421	207	56
PE3422	163	57
PE3423	122	18
PE3424	190	26
PE3425	207	54
PE3426	Web	
PE3427	122	15
PE3428	183	42
PE3429	169	47
PE3430	207	71
PE3434	207	55
PE3435	207	57
PE3436	122	11
PE3440	122	9
PE3441	138	50
PE3443	171	92
PE3444	184	61
PE3445	120	63
PE3447	138	60
PE3448	163	50
PE3449	Web	
PE3450	122	14
PE3451	132	91
PE3453	Web	
PE3455	138	52
PE3457	125	83
PE3458	124	57
PE3459	170	72
PE3462	120	39
PE3465	Web	
PE3466	206	45
PE3468	191	64
PE3472	138	44
PE3476	145	65
PE3477	145	71
PE3478	Web	
PE3479	161	65
PE3480	221	93
PE3481	167	61
PE3483	169	33
PE3485	141	56
PE3487	138	63
PE3488	142	99
PE3490	198	43
PE3492	168	13
PE3494	172	36
PE3495	120	46
PE3496	138	56
PE3497	205	93
PE3498	205	2
PE3499	139	76
PE3500	167	83
PE3501	Web	
PE3504	207	69
PE3505	125	75
PE3508	121	88
PE3509	Web	
PE3510	169	44
PE3511	183	40
PE3512	169	41
PE3513	169	48
PE3514	183	37
PE3515	183	43
PE3516	131	64
PE3517	132	76
PE3518	125	85
PE3519	163	58
PE3520	192	87
PE3521	190	22
PE3522	125	86
PE3524	190	25
PE3525	195	46
PE3526	Web	
PE3528	220	61
PE3531	173	51
PE3534	189	8
PE3535	177	58
PE3536	Web	
PE3539	161	66
PE3542	131	75
PE3543	212	98
PE3544	207	53
PE3545	125	93
PE3546	Web	
PE3548	174	83
PE3550	Web	
PE3551	205	95
PE3553	172	40
PE3557	122	16

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE3675	125	77
PE3678	120	64
PE3679	185	96
PE3680	Web	
PE3681	181	79
PE3683	Web	
PE3684	206	47
PE3686	143	9
PE3689	121	83
PE3690	Web	
PE3693	Web	
PE3694	131	70
PE3695	Web	
PE3696	160	53
PE3697	171	1
PE3698	150	20
PE3699	140	18
PE3700	Web	
PE3701	Web	
PE3704	167	82
PE3706	171	99
PE3708	Web	
PE3713	183	45
PE3714	141	58
PE3715	171	97
PE3721	196	73
PE3722	174	85
PE3724	Web	
PE3725	Web	
PE3726	140	20
PE3729	Web	
PE3733	181	74
PE3735	131	69
PE3736	175	2
PE3739	168	1
PE3740	186	6
PE3741	Web	
PE3743	213	10
PE3744	Web	
PE3747	207	60
PE3749	120	50
PE3750	145	63
PE3753	Web	
PE3755	174	84
PE3758	189	18
PE3759	185	79
PE3764	192	95
PE3765	200	82
PE3767	Web	
PE3769	165	19
PE3770	Web	
PE3775	183	38
PE3776	120	40
PE3777	122	96
PE3778	167	76
PE3779	169	46
PE3780	181	70
PE3781	151	24
PE3782	139	86
PE3785	Web	
PE3792	122	6
PE3794	192	78
PE3795	Web	
PE3796	213	7
PE3797	140	24
PE3799	173	44
PE3800	185	85
PE3803	212	92
PE3806	173	48
PE3807	120	41
PE3808	199	50
PE3809	175	6
PE3810	174	88
PE3814	168	99
PE3815	159	11
PE3816	124	54
PE3817	Web	
PE3818	168	14
PE3819	184	56
PE3820	184	57
PE3821	170	68
PE3822	170	69
PE3823	172	18
PE3824	172	19
PE3825	173	56
PE3826	173	58
PE3827	139	87
PE3828	164	71
PE3829	142	84
PE3830	143	24
PE3832	171	2
PE3834	Web	
PE3835	172	41
PE3836	185	86
PE3838	Web	
PE3842	124	55
PE3843	159	13
PE3845	213	8
PE3850	181	69
PE3852	129	9
PE3853	196	70
PE3857	159	27
PE3858	184	60
PE3864	171	4
PE3865	169	43
PE3867	167	64
PE3869	Web	
PE3871	173	46
PE3873	Web	
PE3874	145	68
PE3876	183	39
PE3882	151	25
PE3883	199	44
PE3884	Web	
PE3887	146	14
PE3894	Web	
PE3895	159	26
PE3896	Web	
PE3898	212	89
PE3899	168	3
PE3902	199	45
PE3903	192	90
PE3904	205	8
PE3906	120	51
PE3907	Web	
PE3908	174	82
PE3910	Web	

Model No.	Page	C/R
PE3911	163	56
PE3914	131	66
PE3915	196	76
PE3916	197	11
PE3917	197	17
PE3918	200	81
PE3919	200	87
PE3920	139	88
PE3921	142	85
PE3922	143	26
PE3924	172	42
PE3925	185	97
PE3928	Web	
PE3929	192	89
PE3930	221	94
PE3931	190	23
PE3932	192	86
PE3935	124	60
PE3936	Web	
PE3940	173	45
PE3944	174	98
PE3945	Web	
PE3946	Web	
PE3948	Web	
PE3949	122	99
PE3950	132	79
PE3953	125	73
PE3956	172	35
PE3957	163	59
PE3958	169	37
PE3959	172	38
PE3960	129	26
PE3961	172	33
PE3963	138	47
PE3965	141	57
PE3966	142	2
PE3967	173	47
PE3971	142	1
PE3972	Web	
PE3973	192	67
PE3976	Web	
PE3977	141	69
PE3979	142	83
PE3980	Web	
PE3982	148	64
PE3983	143	23
PE3986	141	67
PE3987	183	44
PE3988	142	86
PE3989	148	62
PE3991	148	60
PE3992	159	19
PE3993	143	27
PE3994	Web	
PE3995	139	89
PE3996	141	59
PE3997	138	58
PE3999	120	44
PE33001	164	70
PE33002	Web	
PE33003	168	12
PE33004	Web	
PE33006	Web	
PE33009	Web	
PE33013	207	59
PE33014	182	10
PE33018	159	29
PE33021	151	46
PE33022	Web	
PE33024	Web	
PE33035	Web	
PE33039	Web	
PE33042	Web	
PE33046	Web	
PE33047	189	15
PE33053	213	5
PE33062	Web	
PE33064	Web	
PE33065	Web	
PE33068	159	10
PE33069	Web	
PE33071	202	34
PE33073	187	39
PE33077	Web	
PE33084	192	83
PE33091	Web	
PE33094	Web	
PE33098	125	91
PE33103	Web	
PE33112	Web	
PE33117	165	12
PE33120	189	13
PE33121	197	16
PE33123	121	69
PE33124	Web	
PE33125	Web	
PE33126	Web	
PE33130	120	48
PE33132	Web	
PE33143	196	85
PE33144	144	46
PE33151	Web	
PE33154	199	47
PE33155	Web	
PE33158	192	84
PE33159	Web	
PE33165	196	71
PE33170	Web	
PE33174	Web	
PE33175	196	82
PE33176	192	94
PE33178	151	50
PE33179	217	96
PE33181	Web	
PE33185	207	62
PE33188	217	82
PE33189	124	62
PE33191	195	47
PE33194	Web	
PE33195	Web	
PE33196	217	87
PE33197	217	79
PE33208	Web	
PE33220	Web	
PE33221	Web	
PE33225	Web	
PE33234	Web	

Model No.	Page	C/R
PE33236	138	59
PE33237	Web	
PE33243	Web	
PE33247	220	71
PE33252	Web	
PE33253	Web	
PE33254	189	14
PE33257	181	72
PE33258	160	55
PE33260	Web	
PE33261	198	23
PE33266	Web	
PE33267	213	9
PE33269	138	62
PE33270	220	70
PE33271	Web	
PE33272	Web	
PE33275	Web	
PE33278	Web	
PE33280	Web	
PE33284	Web	
PE33285	Web	
PE33288	138	64
PE33298	Web	
PE33300	Web	
PE33304	129	8
PE33307	Web	
PE33316	125	82
PE33318	Web	
PE33320	Web	
PE33321	140	31
PE33330	221	76
PE33342	Web	
PE33345	Web	
PE33349	198	30
PE33350	197	12
PE33352	199	69
PE33355	Web	
PE33356	196	83
PE33361	176	55
PE33363	199	62
PE33365	Web	
PE33367	Web	
PE33370	129	14
PE33377	138	71
PE33380	Web	
PE33381	Web	
PE33382	192	82
PE33384	Web	
PE33391	208	85
PE33393	Web	
PE33394	Web	
PE33396	177	63
PE33399	217	81
PE33400	Web	
PE33401	217	83
PE33405	217	84
PE33407	217	86
PE33412	217	89
PE33414	217	90
PE33417	217	95
PE33420	177	80
PE33421	217	97
PE33425	217	98
PE33426	217	1
PE33430	217	2
PE33432	217	3
PE33434	218	4
PE33437	217	91
PE33438	212	91
PE33439	217	92
PE33440	Web	
PE33442	Web	
PE33443	217	93
PE33445	217	94
PE33446	Web	
PE33448	218	5
PE33449	Web	
PE33450	218	6
PE33451	218	7
PE33455	148	57
PE33456	218	8
PE33457	148	58
PE33465	Web	
PE33469	Web	
PE33471	Web	
PE33474	Web	
PE33476	198	18
PE33479	139	77
PE33481	165	7
PE33482	185	4
PE33484	Web	
PE33485	Web	
PE33486	Web	
PE33488	Web	
PE33491	129	24
PE33493	Web	
PE33494	Web	
PE33495	Web	
PE33502	195	55
PE33503	Web	
PE33505	Web	
PE33510	Web	
PE33513	Web	
PE33516	132	84
PE33518	192	93
PE33519	160	59
PE33521	160	62
PE33523	160	57
PE33525	138	55
PE33527	138	54
PE33528	152	56
PE33529	Web	
PE33530	143	13
PE33532	152	55
PE33534	143	11
PE33535	205	5
PE33536	151	51
PE33537	129	25
PE33539	130	28
PE33541	129	23
PE33542	Web	
PE33543	143	7
PE33545	151	49
PE33546	Web	
PE33547	189	11
PE33548	Web	

Model No.	Page	C/R
PE33551	Web	
PE33552	Web	
PE33554	Web	
PE33555	165	9
PE33556	199	56
PE33557	Web	
PE33559	Web	
PE33561	Web	
PE33563	Web	
PE33565	Web	
PE33567	Web	
PE33574	121	71
PE33575	Web	
PE33580	199	68
PE33581	Web	
PE33583	129	15
PE33584	Web	
PE33586	221	77
PE33590	Web	
PE33596	Web	
PE33601	Web	
PE33603	Web	
PE33605	220	52
PE33606	Web	
PE33615	148	52
PE33628	Web	
PE33632	Web	
PE33633	Web	
PE33634	Web	
PE33635	Web	
PE33636	Web	
PE33641	198	42
PE33643	200	79
PE33644	220	72
PE33645	200	80
PE33646	221	78
PE33647	199	49
PE33649	200	86
PE33650	196	68
PE33652	196	69
PE33654	197	9
PE33656	197	10
PE33657	174	89
PE33658	199	54
PE33659	Web	
PE33660	199	55
PE33662	125	94
PE33664	199	61
PE33666	196	80
PE33668	196	81
PE33669	176	49
PE33670	196	87
PE33672	196	88
PE33673	176	56
PE33674	197	94
PE33675	198	29
PE33676	197	95
PE33680	Web	
PE33682	198	27
PE33686	199	70
PE33688	199	72
PE33690	199	74
PE33692	200	97
PE33698	Web	
PE33700	202	33
PE33701	205	1
PE33704	196	77
PE33706	159	15
PE33710	Web	
PE33714	Web	
PE33716	Web	
PE33720	138	49
PE33721	Web	
PE33725	Web	
PE33728	141	66
PE33733	Web	
PE33737	Web	
PE33749	185	88
PE33751	Web	
PE33752	Web	
PE33753	Web	
PE33758	Web	
PE33759	187	40
PE33762	202	32
PE33764	Web	
PE33772	Web	
PE33774	Web	
PE33777	Web	
PE33778	129	17
PE33786	Web	
PE33789	192	88
PE33793	Web	
PE33794	Web	
PE33795	Web	
PE33799	210	53
PE33801	Web	
PE33803	Web	
PE33825	195	60
PE33831	Web	
PE33837	196	66
PE33840	Web	
PE33844	165	99
PE33853	Web	
PE33862	Web	
PE33864	192	79
PE33867	208	96
PE33876	162	20
PE33887	Web	
PE33889	181	78
PE33896	172	17
PE33927	148	48
PE33928	176	47
PE33929	165	10
PE33935	Web	
PE33938	129	19
PE33939	Web	
PE33944	Web	
PE33948	177	62
PE33953	Web	
PE33954	Web	
PE33957	Web	
PE33959	Web	
PE33960	Web	
PE33964	189	9
PE33969	205	99
PE33974	150	19
PE33975	Web	

Model No.	Page	C/R
PE33977	150	16
PE33978	Web	
PE33982	Web	
PE33984	132	88
PE33989	161	64
PE33996	165	98
PE33998	Web	
PE34008	160	50
PE34035	119	25
PE34036	Web	
PE34046	Web	
PE34050	Web	
PE34057	Web	
PE34061	185	87
PE34062	Web	
PE34069	162	25
PE34070	192	80
PE34071	192	91
PE34078	200	93
PE34087	Web	
PE34098	144	42
PE34106	Web	
PE34111	Web	
PE34116	173	62
PE34119	Web	
PE34122	162	28
PE34123	Web	
PE34129	Web	
PE34135	185	1
PE34138	139	84
PE34140	139	85
PE34141	185	84
PE34142	139	82
PE34143	165	16
PE34144	139	83
PE34146	138	41
PE34148	165	14
PE34149	138	42
PE34150	142	98
PE34151	165	15
PE34152	143	19
PE34153	165	96
PE34154	143	20
PE34155	165	17
PE34156	142	97
PE34157	165	18
PE34158	143	21
PE34159	166	21
PE34160	185	99
PE34161	143	22
PE34162	120	61
PE34163	165	97
PE34164	120	60
PE34165	Web	
PE34166	120	38
PE34168	120	59
PE34169	166	22
PE34170	120	62
PE34171	165	3
PE34173	120	37
PE34174	165	4
PE34175	120	65
PE34176	165	5
PE34177	120	58
PE34178	165	13
PE34179	185	83
PE34180	168	9
PE34181	143	6
PE34182	168	11
PE34183	165	11
PE34184	168	15
PE34185	165	6
PE34186	167	59
PE34188	167	60
PE34191	168	5
PE34193	168	6
PE34194	143	10
PE34195	170	65
PE34197	169	31
PE34198	143	12
PE34199	170	66
PE34200	170	70
PE34201	143	5
PE34202	169	32
PE34203	140	27
PE34204	170	61
PE34205	140	22
PE34206	170	62
PE34207	140	29
PE34208	184	53
PE34209	183	28
PE34210	140	28
PE34211	184	49
PE34212	140	23
PE34213	184	54
PE34214	151	53
PE34215	184	58
PE34216	151	44
PE34217	183	29
PE34218	151	48
PE34219	184	50
PE34220	170	67
PE34221	151	52
PE34222	151	26
PE34223	184	55
PE34224	171	11
PE34226	172	12
PE34227	152	54
PE34228	171	90
PE34229	151	47
PE34230	172	20
PE34231	150	21
PE34232	Web	
PE34233	171	91
PE34235	172	15
PE34236	151	27
PE34237	172	16
PE34238	150	22
PE34240	135	79
PE34241	173	49
PE34243	173	50
PE34244	Web	
PE34245	172	29
PE34246	177	60
PE34247	173	59
PE34248	176	54
PE34249	172	30

Model No.	Page	C/R
PE34250	177	72
PE34252	173	53
PE34253	177	61
PE34254	173	54
PE34255	177	74
PE34256	173	55
PE34257	164	66
PE34259	164	72
PE34261	164	67
PE34263	163	49
PE34265	164	68
PE34266	148	63
PE34268	163	48
PE34269	196	78
PE34270	164	69
PE34271	207	83
PE34272	148	56
PE34273	207	79
PE34274	141	63
PE34275	208	86
PE34276	141	64
PE34277	207	80
PE34279	207	81
PE34280	206	43
PE34281	141	68
PE34282	206	44
PE34283	141	60
PE34284	207	82
PE34285	142	82
PE34287	142	79
PE34289	142	81
PE34291	141	54
PE34292	189	10
PE34293	141	55
PE34296	142	80
PE34297	185	93
PE34299	184	74
PE34303	185	91
PE34305	185	92
PE34307	184	72
PE34309	185	89
PE34311	185	94
PE34312	Web	
PE34313	184	76
PE34314	Web	
PE34315	185	95
PE34316	207	61
PE34317	185	98
PE34319	184	73
PE34321	185	90
PE34323	179	34
PE34324	Web	
PE34331	173	64
PE34333	Web	
PE34345	Web	
PE34346	Web	
PE34351	182	9
PE34357	144	47
PE34359	144	48
PE34360	109	83
PE34361	179	28
PE34366	Web	
PE34370	Web	
PE34374	162	26
PE34383	Web	
PE34385	Web	
PE34387	Web	
PE34393	Web	
PE34396	178	6
PE34397	178	5
PE34398	173	67
PE34405	189	17
PE34406	177	76
PE34407	132	86
PE34408	177	82
PE34409	132	89
PE34410	177	75
PE34411	132	85
PE34412	176	45
PE34413	132	80
PE34414	177	77
PE34415	132	83
PE34416	176	48
PE34417	132	87
PE34418	177	78
PE34419	132	82
PE34420	177	81
PE34421	159	20
PE34422	176	46
PE34423	131	71
PE34424	159	24
PE34425	131	74
PE34427	131	67
PE34428	159	12
PE34429	131	65
PE34430	159	16
PE34431	131	68
PE34432	159	22
PE34433	131	72
PE34434	129	10
PE34435	125	95
PE34436	129	20
PE34437	125	88
PE34438	129	21
PE34439	158	99
PE34440	125	84
PE34441	159	8
PE34442	125	89
PE34443	158	97
PE34446	Web	
PE34447	158	5
PE34448	174	86
PE34449	159	9
PE34450	175	4
PE34452	174	90
PE34453	159	7
PE34454	175	8
PE34455	174	79
PE34456	175	7
PE34458	175	3
PE34459	200	89
PE34460	174	96
PE34461	198	19
PE34462	200	88
PE34463	197	14
PE34464	200	84
PE34465	197	8

Model No.	Page	C/R
PE34466	200	78
PE34467	198	24
PE34469	198	21
PE34470	200	94
PE34471	198	22
PE34472	200	99
PE34473	198	28
PE34474	200	1
PE34475	198	31
PE34476	200	91
PE34477	198	26
PE34478	200	92
PE34479	198	20
PE34480	200	98
PE34481	196	90
PE34482	200	2
PE34483	197	2
PE34484	200	96
PE34485	196	89
PE34486	200	90
PE34487	197	1
PE34488	196	67
PE34489	197	97
PE34490	196	79
PE34491	197	91
PE34492	199	57
PE34493	197	92
PE34494	199	52
PE34495	197	93
PE34496	199	64
PE34497	197	99
PE34498	200	76
PE34499	199	59
PE34500	199	71
PE34501	198	41
PE34502	199	53
PE34503	199	66
PE34504	205	92
PE34505	199	67
PE34507	199	73
PE34508	205	11
PE34509	199	65
PE34510	205	10
PE34511	199	75
PE34518	199	63
PE34520	209	17
PE34523	Web	
PE34532	Web	
PE34538	130	27
PE34539	Web	
PE34544	Web	
PE34548	Web	
PE34553	Web	
PE34554	149	79
PE34559	Web	
PE34560	Web	
PE34562	Web	
PE34568	Web	
PE34570	101	94
PE34571	Web	
PE34572	101	92
PE34573	149	80
PE34574	101	95
PE34575	179	37
PE34576	101	93
PE34578	101	4
PE34579	212	96
PE34580	101	2
PE34581	212	87
PE34582	101	5
PE34583	212	90
PE34584	101	3
PE34585	212	94
PE34586	102	8
PE34587	212	99
PE34588	101	6
PE34589	212	93
PE34590	102	9
PE34591	212	97
PE34592	102	7
PE34595	Web	
PE34598	135	75
PE34599	135	76
PE34600	Web	
PE34604	Web	
PE34612	Web	
PE34613	Web	
PE34614	173	63
PE34617	Web	
PE34618	Web	
PE34621	Web	
PE34622	Web	
PE34623	Web	
PE34626	149	85
PE34649	Web	
PE34666	136	3
PE34669	Web	
PE34670	Web	
PE34674	Web	
PE34675	Web	
PE34679	Web	
PE34680	150	15
PE34681	219	36
PE34683	219	37
PE34685	219	38
PE34686	191	56
PE34687	219	40
PE34689	219	41
PE34690	219	42
PE34691	Web	
PE34692	219	47
PE34693	136	99
PE34694	219	48
PE34696	219	49
PE34698	Web	
PE34701	219	32
PE34703	219	33
PE34704	Web	
PE34705	219	34
PE34707	Web	
PE34708	Web	
PE34709	192	77
PE34713	Web	
PE34715	Web	
PE34716	141	41
PE34717	Web	
PE34721	199	51

Model No.	Page	C/R
PE34727	179	27
PE34729	101	81
PE34730	Web	
PE34731	100	80
PE34733	100	73
PE34742	Web	
PE34743	101	86
PE34745	101	85
PE34750	179	38
PE34752	Web	
PE34754	Web	
PE34755	Web	
PE34757	Web	
PE34759	Web	
PE34764	174	78
PE34770	179	33
PE34773	Web	
PE34777	163	30
PE34786	191	53
PE34792	Web	
PE34801	148	41
PE34808	Web	
PE34809	Web	
PE34812	Web	
PE34817	Web	
PE34831	Web	
PE34833	189	7
PE34834	190	21
PE34835	189	19
PE34836	190	20
PE34853	178	1
PE34854	178	2
PE34856	128	97
PE34858	128	98
PE34860	129	99
PE34862	128	94
PE34863	Web	
PE34864	128	95
PE34879	135	74
PE34881	136	83
PE34882	145	73
PE34883	136	84
PE34884	Web	
PE34885	135	77
PE34887	162	27
PE34889	136	85
PE34891	135	78
PE34893	136	86
PE34895	136	87
PE34898	Web	
PE34902	Web	
PE34917	189	16
PE34922	Web	
PE34925	Web	
PE34926	Web	
PE34940	Web	
PE34945	Web	
PE34952	Web	
PE34957	181	80
PE34962	Web	
PE34963	Web	
PE34966	149	78
PE34969	Web	
PE34982	Web	
PE34990	Web	
PE34993	Web	
PE35006	Web	
PE35012	Web	
PE35015	Web	
PE35021	213	2
PE35023	Web	
PE35024	Web	
PE35029	Web	
PE35035	Web	
PE35048	Web	
PE35051	Web	
PE35064	195	45
PE35087	Web	
PE35095	Web	
PE35097	Web	
PE35098	Web	
PE35108	195	43
PE35109	160	51
PE35110	195	52
PE35111	Web	
PE35112	195	51
PE35114	195	44
PE35115	Web	
PE35116	195	53
PE35118	195	54
PE35121	101	97
PE35131	Web	
PE35133	Web	
PE35144	Web	
PE35148	120	45
PE35154	195	42
PE35184	Web	
PE35197	Web	
PE35207	179	18
PE35208	173	65
PE35209	179	19
PE35210	173	66
PE35212	173	68
PE35213	179	21
PE35214	180	40
PE35216	180	41
PE35217	179	23
PE35218	180	42
PE35220	180	43
PE35221	179	29
PE35222	180	44
PE35223	179	30
PE35224	180	45
PE35225	179	31
PE35226	180	46
PE35227	179	32
PE35228	208	8
PE35229	209	14
PE35230	208	9
PE35231	209	15
PE35232	208	10
PE35233	209	16
PE35234	209	11
PE35235	209	18
PE35236	209	12
PE35238	209	13
PE35241	149	81

Appendix

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE35242	178	3
PE35243	149	82
PE35244	178	4
PE35245	149	83
PE35246	178	7
PE35247	149	84
PE35256	119	28
PE35269	144	56
PE35276	145	77
PE35281	Web	
PE35282	Web	
PE35283	109	73
PE35284	144	39
PE35334	Web	
PE35343	Web	
PE35347	183	17
PE35348	221	87
PE35349	180	47
PE35350	221	82
PE35351	173	71
PE35352	221	88
PE35353	180	48
PE35354	221	83
PE35355	173	72
PE35356	221	89
PE35357	180	49
PE35358	221	84
PE35359	174	73
PE35360	221	90
PE35361	180	50
PE35362	221	85
PE35363	174	74
PE35364	221	91
PE35365	180	51
PE35366	221	86
PE35367	174	75
PE35369	180	52
PE35371	174	76
PE35373	180	53
PE35375	174	77
PE35384	159	17
PE35387	Web	
PE35389	Web	
PE35404	192	81
PE35430	175	16
PE35435	Web	
PE35437	Web	
PE35441	Web	
PE35444	Web	
PE35454	Web	
PE35463	131	58
PE35474	Web	
PE35480	210	48
PE35505	Web	
PE35508	179	35
PE35522	136	94
PE35527	174	91
PE35541	Web	
PE35552	Web	
PE35556	Web	
PE35563	Web	
PE35565	Web	
PE35567	Web	
PE35568	Web	
PE35571	167	77
PE35573	Web	
PE35575	191	50
PE35580	175	75
PE35613	Web	
PE35627	Web	
PE35635	210	56
PE35646	Web	
PE35653	Web	
PE35659	Web	
PE35671	207	51
PE35699	Web	
PE35700	Web	
PE35711	207	65
PE35729	119	30
PE35751	Web	
PE35757	Web	
PE35758	Web	
PE35760	Web	
PE35782	Web	
PE35784	166	34
PE35785	148	38
PE35787	Web	
PE35789	205	94
PE35791	Web	
PE35799	132	77
PE35814	Web	
PE35815	Web	
PE35818	Web	
PE35843	Web	
PE35845	Web	
PE35874	119	31
PE35879	Web	
PE35882	Web	
PE35883	Web	
PE35886	206	31
PE35894	Web	
PE35896	Web	
PE35900	109	79
PE35906	Web	
PE35907	Web	
PE35911	Web	
PE35914	Web	
PE35916	Web	
PE35924	Web	
PE35934	Web	
PE35949	Web	
PE35950	Web	
PE35953	128	90
PE35955	128	91
PE35957	128	92
PE35959	128	86
PE35962	128	87
PE35963	144	50
PE35965	144	38
PE35981	163	36
PE35991	187	43
PE35993	Web	
PE35997	206	30
PE36000	Web	
PE36012	Web	
PE36013	Web	
PE36028	Web	

Model No.	Page	C/R
PE36034	Web	
PE36046	Web	
PE36056	Web	
PE36058	176	34
PE36059	Web	
PE36064	Web	
PE36065	144	55
PE36066	119	27
PE36067	148	39
PE36068	204	89
PE36072	179	26
PE36079	Web	
PE36087	Web	
PE36101	Web	
PE36108	162	18
PE36109	216	69
PE36110	162	17
PE36111	216	70
PE36112	162	16
PE36113	216	71
PE36114	130	30
PE36116	130	31
PE36117	216	72
PE36118	130	32
PE36119	216	73
PE36120	130	33
PE36122	130	34
PE36123	217	77
PE36124	130	35
PE36125	217	78
PE36126	130	36
PE36127	216	74
PE36128	130	37
PE36129	216	75
PE36130	130	38
PE36131	216	76
PE36132	218	19
PE36134	109	78
PE36135	218	20
PE36136	109	81
PE36137	218	23
PE36138	109	84
PE36139	218	24
PE36140	109	71
PE36141	218	21
PE36142	109	85
PE36143	218	22
PE36144	109	72
PE36145	218	11
PE36146	201	14
PE36147	218	12
PE36148	201	10
PE36149	218	13
PE36150	201	15
PE36151	218	14
PE36152	201	11
PE36153	218	15
PE36154	201	19
PE36155	218	16
PE36156	201	16
PE36157	160	38
PE36158	201	20
PE36159	160	41
PE36160	201	17
PE36161	160	43
PE36162	201	7
PE36163	160	44
PE36164	175	9
PE36165	160	45
PE36166	175	10
PE36167	160	46
PE36168	201	8
PE36169	160	36
PE36170	144	44
PE36171	160	47
PE36172	144	45
PE36173	160	37
PE36174	110	15
PE36178	144	37
PE36181	139	78
PE36182	Web	
PE36200	163	37
PE36201	170	76
PE36203	Web	
PE36209	Web	
PE36215	Web	
PE36218	Web	
PE36219	119	29
PE36227	Web	
PE36236	Web	
PE36246	Web	
PE36265	Web	
PE36266	Web	
PE36269	Web	
PE36273	138	53
PE36283	149	86
PE36292	Web	
PE36293	Web	
PE36298	Web	
PE36303	Web	
PE36305	Web	
PE36307	Web	
PE36322	Web	
PE36325	Web	
PE36345	124	67
PE36362	149	77
PE36363	Web	
PE36376	Web	
PE36380	Web	
PE36381	Web	
PE36384	Web	
PE36390	Web	
PE36402	Web	
PE36417	172	23
PE36419	Web	
PE36422	Web	
PE36424	Web	
PE36433	Web	
PE36440	Web	
PE36444	Web	
PE36452	Web	
PE36455	124	71
PE36465	Web	
PE36472	Web	
PE36475	169	17
PE36491	Web	
PE36503	Web	

Model No.	Page	C/R
PE36504	Web	
PE36506	Web	
PE36507	181	85
PE36517	Web	
PE36519	97	16
PE36520	112	55
PE36521	97	12
PE36522	112	56
PE36523	97	17
PE36524	112	57
PE36525	97	13
PE36526	112	58
PE36528	112	59
PE36530	112	60
PE36532	113	64
PE36534	113	65
PE36535	101	88
PE36536	113	66
PE36537	101	87
PE36539	159	32
PE36540	113	62
PE36541	159	30
PE36546	Web	
PE36551	Web	
PE36555	206	29
PE36556	Web	
PE36562	Web	
PE36569	202	35
PE36570	202	38
PE36571	202	36
PE36572	202	39
PE36573	202	37
PE36574	202	40
PE36589	138	51
PE36593	Web	
PE36605	Web	
PE36613	Web	
PE36623	Web	
PE36634	136	2
PE36657	109	93
PE36661	160	58
PE36667	Web	
PE36673	Web	
PE36680	Web	
PE36689	167	69
PE36690	167	70
PE36701	Web	
PE36704	Web	
PE36718	Web	
PE36731	Web	
PE36735	Web	
PE36737	Web	
PE36738	136	90
PE36755	Web	
PE36773	Web	
PE36776	Web	
PE36779	211	69
PE36780	Web	
PE36784	Web	
PE36789	Web	
PE36799	130	44
PE36805	Web	
PE36839	Web	
PE36848	177	73
PE36850	Web	
PE36855	Web	
PE36874	Web	
PE36878	Web	
PE36897	Web	
PE36910	150	96
PE36919	Web	
PE36939	Web	
PE36955	Web	
PE36958	148	40
PE36961	Web	
PE36963	173	69
PE36970	Web	
PE36971	Web	
PE36982	Web	
PE36989	Web	
PE37007	Web	
PE37019	Web	
PE37028	Web	
PE37054	Web	
PE37061	Web	
PE37067	Web	
PE37073	Web	
PE37078	Web	
PE37080	Web	
PE37087	Web	
PE37091	Web	
PE37099	131	57
PE37109	Web	
PE37112	Web	
PE37113	Web	
PE37120	178	99
PE37128	Web	
PE37137	208	7
PE37140	Web	
PE37142	Web	
PE37151	Web	
PE37163	218	18
PE37169	Web	
PE37175	Web	
PE37176	Web	
PE37185	Web	
PE37189	Web	
PE37199	Web	
PE37220	Web	
PE37249	Web	
PE37250	196	64
PE37257	Web	
PE37275	Web	
PE37294	Web	
PE37299	Web	
PE37301	Web	
PE37305	Web	
PE37310	Web	
PE37317	Web	
PE37332	Web	
PE37357	148	53
PE37362	Web	
PE37364	Web	
PE37374	Web	
PE37378	Web	
PE37381	Web	
PE37390	Web	

Model No.	Page	C/R
PE37401	175	19
PE37411	Web	
PE37412	Web	
PE37413	Web	
PE37414	Web	
PE37425	Web	
PE37432	Web	
PE37434	Web	
PE37450	110	7
PE37455	Web	
PE37478	205	6
PE37480	Web	
PE37497	111	24
PE37512	Web	
PE37513	Web	
PE37535	Web	
PE37563	204	91
PE37567	Web	
PE37573	Web	
PE37580	176	51
PE37584	Web	
PE37585	Web	
PE37594	204	90
PE37600	109	92
PE37610	Web	
PE37611	Web	
PE37629	Web	
PE37640	124	58
PE37642	Web	
PE37643	Web	
PE37663	Web	
PE37693	Web	
PE37697	Web	
PE37717	Web	
PE37747	Web	
PE37749	Web	
PE37789	Web	
PE37790	Web	
PE37804	Web	
PE37806	Web	
PE37808	217	80
PE37811	Web	
PE37812	Web	
PE37821	Web	
PE37828	Web	
PE37840	215	56
PE37841	216	58
PE37842	215	50
PE37843	215	51
PE37844	215	47
PE37845	215	49
PE37846	215	52
PE37847	215	53
PE37848	157	65
PE37849	216	67
PE37850	215	54
PE37851	215	55
PE37859	205	4
PE37861	Web	
PE37885	204	88
PE37894	Web	
PE37900	173	60
PE37908	166	33
PE37910	Web	
PE37913	Web	
PE37920	Web	
PE37922	Web	
PE37940	136	98
PE37941	136	1
PE37942	136	4
PE37943	136	5
PE37944	139	92
PE37945	139	93
PE37946	139	94
PE37947	139	95
PE37948	140	39
PE37949	141	40
PE37950	141	42
PE37951	141	43
PE37952	108	55
PE37953	108	56
PE37954	108	57
PE37955	108	58
PE37956	109	86
PE37957	109	87
PE37958	109	88
PE37960	110	95
PE37961	110	96
PE37962	110	97
PE37963	110	98
PE37969	141	72
PE37970	140	33
PE37972	110	8
PE37973	109	94
PE37982	Web	
PE37995	170	75
PE38012	Web	
PE38023	Web	
PE38040	219	35
PE38043	Web	
PE38052	189	1
PE38059	168	2
PE38083	Web	
PE38089	Web	
PE38093	181	68
PE38116	166	23
PE38117	Web	
PE38130	217	85
PE38132	217	99
PE38133	220	67
PE38134	220	68
PE38135	220	69
PE38136	218	25
PE38137	218	27
PE38138	219	30
PE38139	219	39
PE38140	219	43
PE38141	219	44
PE38147	Web	
PE38161	157	71
PE38184	192	85
PE38192	Web	
PE38194	150	98
PE38202	Web	
PE38204	152	69
PE38207	Web	
PE38208	Web	

Model No.	Page	C/R
PE38215	Web	
PE38219	Web	
PE38231	135	81
PE38240	172	22
PE38249	124	45
PE38260	Web	
PE38268	Web	
PE38270	157	70
PE38271	157	69
PE38272	157	66
PE38273	166	25
PE38274	166	26
PE38275	166	24
PE38276	189	99
PE38277	189	98
PE38278	189	97
PE38291	Web	
PE38296	216	68
PE38298	213	16
PE38299	194	22
PE38300	194	33
PE38301	195	41
PE38302	213	17
PE38303	212	85
PE38304	212	80
PE38311	Web	
PE38313	Web	
PE38314	Web	
PE38318	Web	
PE38322	136	82
PE38343	218	26
PE38344	121	92
PE38351	Web	
PE38355	Web	
PE38364	Web	
PE38387	Web	
PE38392	Web	
PE38400	Web	
PE38402	Web	
PE38407	202	41
PE38411	Web	
PE38423	Web	
PE38433	163	35
PE38436	143	32
PE38438	Web	
PE38446	158	90
PE38447	158	91
PE38448	158	89
PE38449	158	88
PE38450	146	89
PE38451	146	90
PE38452	146	88
PE38453	146	87
PE38454	154	99
PE38455	154	1
PE38456	154	98
PE38457	154	97
PE38465	Web	
PE38474	Web	
PE38478	Web	
PE38485	158	93
PE38486	158	92
PE38487	158	94
PE38488	158	95
PE38489	146	93
PE38490	146	91
PE38491	146	94
PE38492	146	95
PE38493	154	3
PE38494	154	2
PE38495	154	4
PE38496	154	5
PE38502	213	14
PE38506	124	59
PE38511	Web	
PE38515	Web	
PE38517	Web	
PE38533	Web	
PE38543	Web	
PE38547	Web	
PE38549	Web	
PE38574	184	67
PE38584	109	91
PE38589	Web	
PE38592	Web	
PE38603	Web	
PE38617	Web	
PE38623	Web	
PE38624	169	18
PE38627	Web	
PE38628	166	35
PE38632	213	1
PE38638	170	77
PE38642	176	35
PE38644	Web	
PE38645	163	38
PE38651	Web	
PE38670	151	43
PE38671	Web	
PE38672	142	89
PE38674	212	86
PE38679	135	80
PE38689	Web	
PE38699	150	97
PE38714	Web	
PE38719	128	89
PE38725	Web	
PE38740	Web	
PE38746A	127	55
PE38746B	127	57
PE38746C	127	58
PE38746D	127	59
PE38746H	127	60
PE38746I	127	61
PE38746K	127	62
PE38746Z	127	56
PE38747A	125	96
PE38747C	125	97
PE38747D	125	98
PE38747H	125	99
PE38747I	125	1
PE38747K	125	2
PE38747Z	126	3
PE38748A	126	18
PE38748C	126	19
PE38748D	126	20
PE38748H	126	21

Model No.	Page	C/R
PE38748I	126	22
PE38748K	126	23
PE38748Z	126	24
PE38749A	126	33
PE38749B	126	34
PE38749C	126	35
PE38749D	126	36
PE38749H	126	37
PE38749I	126	38
PE38749K	126	39
PE38749Z	126	40
PE38750A	127	63
PE38750B	127	64
PE38750C	127	65
PE38750D	127	66
PE38750H	127	67
PE38750I	127	68
PE38750K	127	69
PE38750Z	127	70
PE38751A	126	4
PE38751C	126	5
PE38751D	126	6
PE38751H	126	7
PE38751I	126	8
PE38751K	126	9
PE38751Z	126	10
PE38752A	126	26
PE38752C	126	27
PE38752D	126	28
PE38752H	126	29
PE38752I	126	30
PE38752K	126	31
PE38752Z	126	32
PE38753A	127	41
PE38753C	127	42
PE38753D	127	43
PE38753H	127	44
PE38753I	127	45
PE38753K	127	46
PE38753Z	127	47
PE38754A	127	72
PE38754B	127	73
PE38754C	127	74
PE38754D	127	75
PE38754H	127	76
PE38754I	128	77
PE38754K	128	78
PE38754Z	128	79
PE38755A	126	11
PE38755C	126	12
PE38755D	126	13
PE38755H	126	14
PE38755I	126	15
PE38755K	126	16
PE38755Z	126	17
PE38756B	Web	
PE38756C	Web	
PE38756D	Web	
PE38756H	Web	
PE38756I	Web	
PE38756K	Web	
PE38756Z	Web	
PE38757A	127	48
PE38757C	127	49
PE38757D	127	50
PE38757H	127	51
PE38757I	127	52
PE38757K	127	53
PE38757Z	128	85
PE38762	Web	
PE38763	Web	
PE38772	Web	
PE38781	Web	
PE38795	Web	
PE38804	122	8
PE38813	149	87
PE38823	Web	
PE38826	Web	
PE38830	206	49
PE38838	Web	
PE38842	Web	
PE38849	Web	
PE38853	Web	
PE38858	128	93
PE38881	178	9
PE38889	213	15
PE38890	213	13
PE38898	Web	
PE38907	Web	
PE38920	183	18
PE38927	Web	
PE38930	213	19
PE38934	139	91
PE38943	Web	
PE38953	Web	
PE38997	121	73
PE39010	Web	
PE39028	Web	
PE39035	201	4
PE39051	Web	
PE39061	Web	
PE39062	Web	
PE39063	Web	
PE39074	Web	
PE39078	213	18
PE39081	Web	
PE39082	151	42
PE39087	167	67
PE39108	121	87
PE39112	Web	
PE39113	Web	
PE39118	Web	
PE39120	197	7
PE39128	Web	
PE39132	Web	
PE39138	181	75
PE39143	143	31
PE39148	170	78
PE39171	Web	
PE39183	Web	
PE39185	124	44
PE39197A	161	77
PE39197C	161	78
PE39197D	161	79
PE39197H	161	80
PE39197I	161	81
PE39197K	161	82

Model No.	Page	C/R
PE39197Z	161	83
PE39199A	162	99
PE39199B	162	1
PE39199C	162	2
PE39199D	162	3
PE39199H	162	4
PE39199I	162	5
PE39199K	162	6
PE39199Z	162	7
PE39229	159	25
PE39231	Web	
PE39242	Web	
PE39243	Web	
PE39255	205	97
PE39256	Web	
PE39258	Web	
PE39260	Web	
PE39275	Web	
PE39277	Web	
PE39278	Web	
PE39298	Web	
PE39301	Web	
PE39315	Web	
PE39318	Web	
PE39324	Web	
PE39326	Web	
PE39332	Web	
PE39333	Web	
PE39340	Web	
PE39342A	161	69
PE39342B	161	70
PE39342C	161	71
PE39342D	161	72
PE39342H	161	73
PE39342I	161	74
PE39342K	161	75
PE39342Z	161	76
PE39343A	161	84
PE39343C	161	85
PE39343D	161	86
PE39343H	161	87
PE39343I	161	88
PE39343K	161	89
PE39343Z	161	90
PE39344A	187	46
PE39344C	187	47
PE39344D	187	48
PE39344H	187	49
PE39344I	187	50
PE39344K	187	51
PE39344Z	187	52
PE39345A	187	53
PE39345C	187	54
PE39345D	187	55
PE39345H	187	56
PE39345I	187	57
PE39345K	187	58
PE39345Z	188	59
PE39346A	188	60
PE39346C	188	61
PE39346D	188	62
PE39346H	188	63
PE39346I	188	64
PE39346K	188	65
PE39346Z	188	66
PE39347A	161	91
PE39347B	161	92
PE39347C	161	93
PE39347D	161	94
PE39347H	161	95
PE39347I	161	96
PE39347K	161	97
PE39347Z	162	98
PE39348A	162	8
PE39348B	162	9
PE39348C	162	10
PE39348D	162	11
PE39348H	162	12
PE39348I	162	13
PE39348K	162	14
PE39348Z	162	15
PE39349A	188	67
PE39349B	188	68
PE39349C	188	69
PE39349D	188	70
PE39349H	188	71
PE39349I	188	72
PE39349K	188	73
PE39349Z	188	74
PE39350A	188	75
PE39350B	188	76
PE39350C	188	77
PE39350D	188	78
PE39350H	188	79
PE39350I	188	80
PE39350K	188	81
PE39350Z	188	82
PE39351A	188	83
PE39351B	188	84
PE39351C	188	85
PE39351D	188	86
PE39351H	188	87
PE39351I	188	88
PE39351K	188	89
PE39351Z	128	83
PE39395	Web	
PE39415	167	65
PE39416	183	34
PE39417	169	36
PE39418	171	84
PE39419	172	32
PE39420	184	77
PE39421	191	48
PE39422	191	51
PE39423	167	62
PE39424	183	31
PE39425	169	34
PE39426	171	83
PE39427	191	65
PE39428	184	69
PE39429	167	66
PE39430	183	35
PE39431	182	14
PE39432	171	85
PE39433	172	34
PE39434	190	43
PE39435	191	49

Model No.	Page	C/R
PE39436	191	52
PE39437	167	63
PE39438	183	32
PE39439	169	35
PE39440	171	93
PE39441	172	31
PE39442	184	70
PE39443	138	46
PE39444	150	7
PE39445	140	8
PE39446	141	47
PE39447	165	93
PE39448	182	7
PE39449	155	23
PE39450	155	25
PE39451	138	45
PE39452	150	17
PE39453	139	7
PE39454	141	46
PE39455	165	91
PE39456	182	4
PE39457	137	27
PE39458	150	8
PE39459	140	9
PE39460	153	87
PE39461	165	94
PE39462	182	8
PE39463	155	24
PE39464	155	26
PE39465	137	26
PE39466	150	18
PE39467	140	17
PE39468	153	88
PE39469	165	92
PE39470	182	5
PE39471	206	40
PE39472	210	38
PE39473	209	30
PE39474	208	98
PE39475	178	94
PE39476	187	36
PE39477	210	51
PE39478	210	54
PE39479	206	39
PE39480	210	40
PE39481	208	92
PE39482	210	47
PE39483	178	96
PE39484	187	34
PE39485	206	48
PE39486	210	39
PE39487	208	94
PE39488	208	99
PE39489	178	95
PE39490	187	38
PE39491	210	52
PE39492	210	55
PE39493	206	46
PE39494	210	37
PE39495	208	93
PE39496	208	1
PE39497	178	97
PE39498	187	35
PE39520	Web	
PE39521	Web	
PE39547	Web	
PE39548	Web	
PE39564	163	29
PE39570	Web	
PE39571	Web	
PE39599	221	92
PE39619	Web	
PE39635	Web	
PE39639A	Web	
PE39651	Web	
PE39660	Web	
PE39667	Web	
PE39679	Web	
PE39701	Web	
PE39702	Web	
PE39707	Web	
PE39710	Web	
PE39719	Web	
PE39723	Web	
PE39727	Web	
PE39730	Web	
PE39755	Web	
PE39784	Web	
PE39790	Web	
PE39809	Web	
PE39846	Web	
PE39869	Web	
PE39876	Web	
PE39884	Web	
PE39947	Web	
PE39968	Web	
PE39970	Web	
PE39976	Web	
PE39981	Web	
PE39985	Web	
PE39991	Web	
PE3C0031	148	42
PE3C0033	137	9
PE3C0038	166	28
PE3C0039	136	6
PE3C0040	161	68
PE3C0041	139	96
PE3C0042	206	33
PE3C0044	163	39
PE3C0045	189	4
PE3C0046	137	10
PE3C0047	205	12
PE3C0048	137	12
PE3C0049	145	84
PE3C0050	139	1
PE3C0051	160	49
PE3C0052	166	37
PE3C0053	136	7
PE3C0054	119	26
PE3C0056	186	29
PE3C0057	166	36
PE3C0058	208	87
PE3C0059	146	92
PE3C0060	137	16
PE3C0061	137	17
PE3C0062	137	13
PE3C0063	157	63

Appendix

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE3C0064	195	50
PE3C0101	137	8
PE3C0102	163	31
PE3C0103	166	38
PE3C0104	169	19
PE3C0105	137	11
PE3C0106	139	97
PE3C0107	150	99
PE3C0109	148	43
PE3C0110	137	14
PE3C0111	139	2
PE3C0112	137	15
PE3C0113	166	27
PE3C0116	168	88
PE3C0117	206	34
PE3C0118	136	95
PE3C0119	150	1
PE3C0120	150	94
PE3C0121	163	33
PE3C0124	136	96
PE3C0125	142	87
PE3C0126	153	94
PE3C0218	138	72
PE3C0230	166	40
PE3C0231	137	19
PE3C0252	164	64
PE3C0253	146	97
PE3C0438	201	18
PE3C0441	97	3
PE3C0481	179	25
PE3C0631	207	68
PE3C0666	100	75
PE3C0673	151	36
PE3C0689	163	41
PE3C0752	97	14
PE3C0757	201	13
PE3C0780	177	83
PE3C0806	169	25
PE3C0835	100	67
PE3C0847	176	38
PE3C0967	150	2
PE3C1000	155	32
PE3C1015	168	10
PE3C1037	164	74
PE3C1041	209	20
PE3C1081	191	57
PE3C1084	156	50
PE3C1110	156	48
PE3C1128	147	22
PE3C1144	209	32
PE3C1173	186	30
PE3C1179	186	16
PE3C1203	183	47
PE3C1239	189	5
PE3C1271	152	66
PE3C1316	149	92
PE3C1377	100	74
PE3C1398	166	31
PE3C1409	186	23
PE3C1425	183	19
PE3C1528	182	93
PE3C1617	186	21
PE3C1722	169	29
PE3C1830	160	48
PE3C1876	171	5
PE3C1982	163	32
PE3C1988	200	77
PE3C2000	96	94
PE3C2001	96	95
PE3C2002	96	92
PE3C2003	96	57
PE3C2004	96	58
PE3C2005	96	93
PE3C2006	96	96
PE3C2007	96	74
PE3C2008	96	75
PE3C2009	96	26
PE3C2010	96	27
PE3C2011	96	99
PE3C2012	96	97
PE3C2013	96	59
PE3C2014	96	98
PE3C2015	96	60
PE3C2034	120	49
PE3C2035	160	56
PE3C2162	164	87
PE3C2180	211	76
PE3C2220	120	36
PE3C2275	123	26
PE3C2276	149	74
PE3C2295	120	47
PE3C2305	184	63
PE3C2360	160	61
PE3C2404	144	57
PE3C2416	120	54
PE3C2449	178	91
PE3C2578	198	36
PE3C2599	198	38
PE3C2604	186	28
PE3C2884	183	27
PE3C2892	173	57
PE3C2953	151	41
PE3C2985	182	99
PE3C2998	113	67
PE3C3023	196	63
PE3C3028	175	13
PE3C3055	166	29
PE3C3115	151	33
PE3C3159	189	95
PE3C3205	190	39
PE3C3221	201	22
PE3C3232	155	37
PE3C3233	150	14
PE3C3234	153	93
PE3C3235	167	57
PE3C3236	164	78
PE3C3237	164	84
PE3C3238	181	89
PE3C3240	140	16
PE3C3241	141	53
PE3C3242	176	44
PE3C3243	152	64
PE3C3244	154	9
PE3C3245	182	6
PE3C3246	165	95
PE3C3247	153	95
PE3C3248	169	30

Model No.	Page	C/R
PE3C3249	182	97
PE3C3250	182	98
PE3C3251	164	79
PE3C3252	164	85
PE3C3255	143	15
PE3C3275	113	61
PE3C2779	126	25
PE3C3286	143	25
PE3C3314	124	63
PE3C3318	195	59
PE3C3321	161	67
PE3C3325	122	97
PE3C3328	160	54
PE3C3332	179	20
PE3C3344	122	3
PE3C3349	121	68
PE3C3350	181	76
PE3C3354	164	65
PE3C3375	121	89
PE3C3377	121	80
PE3C3378	144	61
PE3C3379	144	62
PE3C3380	145	66
PE3C3387	130	39
PE3C3391	121	84
PE3C3393	205	3
PE3C3397	122	12
PE3C3399	122	13
PE3C3400	205	96
PE3C3401	205	98
PE3C3404	121	79
PE3C3409	128	96
PE3C3412	179	22
PE3C3413	179	24
PE3C3414	209	19
PE3C3420	128	88
PE3C3424	113	63
PE3C3425	198	35
PE3C3428	195	61
PE3C3437	181	73
PE3C3446	122	17
PE3C3448	181	71
PE3C3453	122	98
PE3C3469	97	2
PE3C3583	215	48
PE3C6275	127	54
PE3C3643	140	35
PE3C3741	121	91
PE3C3821	191	54
PE3C3854	133	16
PE3C3922	133	27
PE3C3937	193	99
PE3C3985	132	1
PE3C3986	133	5
PE3C3987	134	41
PE3C3989	133	14
PE3C3990	134	50
PE3C3991	134	31
PE3C3992	135	67
PE3C3993	133	9
PE3C3994	134	45
PE3C3995	134	36
PE3C3996	135	71
PE3C3997	133	18
PE3C3998	134	54
PE3C3999	133	22
PE3C4000	144	49
PE3C4000-60	350	37
PE3C4000-144	350	37
PE3C4001	144	54
PE3C4001-60	350	38
PE3C4001-144	350	38
PE3C4002	138	73
PE3C4002-60	350	39
PE3C4002-144	350	39
PE3C4003	140	36
PE3C4003-60	350	40
PE3C4003-144	350	40
PE3C4004	142	73
PE3C4004-60	350	41
PE3C4004-144	350	41
PE3C4005	138	74
PE3C4005-100CM	350	42
PE3C4006	140	37
PE3C4006-100CM	350	43
PE3C4007	142	74
PE3C4007-100CM	350	44
PE3C4008	146	8
PE3C4008-60	350	45
PE3C4009	147	24
PE3C4009-60	350	46
PE3C4010	148	66
PE3C4010-60	350	47
PE3C4011	149	73
PE3C4011-60	350	48
PE3C4012	101	99
PE3C4012-100CM	350	49
PE3C4013	102	10
PE3C4013-100CM	350	50
PE3C4014	132	2
PE3C4015	133	6
PE3C4016	134	42
PE3C4017	133	28
PE3C4018	135	64
PE3C4019	133	15
PE3C4020	134	51
PE3C4021	134	32
PE3C4022	135	68
PE3C4023	133	10
PE3C4024	134	46
PE3C4025	134	37
PE3C4026	135	72
PE3C4027	133	19
PE3C4028	135	55
PE3C4029	133	23
PE3C4030	135	59
PE3C4031	132	99
PE3C4032	133	4
PE3C4033	134	40
PE3C4034	133	26
PE3C4035	135	62
PE3C4036	133	13
PE3C4037	134	49
PE3C4038	134	30
PE3C4039	135	66
PE3C4040	133	8
PE3C4041	134	44

Model No.	Page	C/R
PE3C4042	134	35
PE3C4043	135	70
PE3C4044	133	17
PE3C4045	134	53
PE3C4046	133	21
PE3C4047	135	57
PE3C4048	132	3
PE3C4049	133	7
PE3C4050	134	43
PE3C4051	133	29
PE3C4052	135	65
PE3C4053	134	52
PE3C4054	134	33
PE3C4055	135	69
PE3C4056	133	11
PE3C4057	134	47
PE3C4058	134	38
PE3C4059	135	73
PE3C4060	133	20
PE3C4061	135	56
PE3C4062	133	24
PE3C4063	135	60
PE3C4064	132	98
PE3C4065	134	39
PE3C4066	133	25
PE3C4067	135	61
PE3C4068	133	12
PE3C4069	134	48
PE3C4130	96	44
PE3C4131	96	52
PE3C4132	96	78
PE3C4133	96	89
PE3C4134	96	5
PE3C4135	96	30
PE3C4136	96	79
PE3C4137	96	80
PE3C4138	96	90
PE3C4139	96	87
PE3C4140	96	76
PE3C4141	96	77
PE3C4142	96	28
PE3C4143	96	1
PE3C4144	96	53
PE3C4145	96	88
PE3C4146	96	39
PE3C4147	96	38
PE3C4164	176	36
PE3C4238	155	38
PE3C4341	201	12
PE3C4374	204	71
PE3C4386	115	12
PE3C4388	203	54
PE3C4389	203	61
PE3C4390	204	83
PE3C4391	175	22
PE3C4392	176	33
PE3C4393	190	30
PE3C4394	190	36
PE3C4395	193	3
PE3C4396	193	11
PE3C4397	123	33
PE3C4398	123	42
PE3C4399	147	30
PE3C4400	147	37
PE3C4401	203	65
PE3C4402	204	86
PE3C4403	203	55
PE3C4404	203	59
PE3C4405	175	24
PE3C4406	176	29
PE3C4407	186	9
PE3C4408	186	13
PE3C4409	190	31
PE3C4410	190	34
PE3C4411	193	4
PE3C4412	193	8
PE3C4413	123	34
PE3C4414	123	39
PE3C4415	147	27
PE3C4416	147	34
PE3C4417	203	66
PE3C4418	204	79
PE3C4419	203	52
PE3C4420	203	56
PE3C4421	203	68
PE3C4422	175	20
PE3C4423	175	26
PE3C4424	186	7
PE3C4425	186	11
PE3C4426	190	29
PE3C4427	190	32
PE3C4428	193	1
PE3C4429	193	5
PE3C4430	123	31
PE3C4431	123	36
PE3C4432	147	28
PE3C4433	147	31
PE3C4434	203	63
PE3C4435	204	76
PE3C4437	175	25
PE3C4438	186	10
PE3C4441	203	53
PE3C4442	203	60
PE3C4443	204	82
PE3C4444	175	21
PE3C4445	176	32
PE3C4446	186	8
PE3C4447	186	15
PE3C4448	193	2
PE3C4449	193	10
PE3C4450	123	32
PE3C4451	147	29
PE3C4452	147	36
PE3C4453	203	64
PE3C4454	204	85
PE3C4455	203	58
PE3C4457	204	70
PE3C4458	204	74
PE3C4459	203	62
PE3C4460	204	75
PE3C4461	204	84
PE3C4462	204	87
PE3C4463	176	28
PE3C4464	190	33
PE3C4465	193	7
PE3C4466	123	38
PE3C4467	147	33

Model No.	Page	C/R
PE3C4468	204	78
PE3C4470	204	72
PE3C4471	176	30
PE3C4472	186	14
PE3C4473	190	35
PE3C4474	193	9
PE3C4475	123	35
PE3C4476	123	40
PE3C4478	147	35
PE3C4480	204	80
PE3C4481	203	57
PE3C4482	203	69
PE3C4483	204	73
PE3C4484	175	27
PE3C4485	186	12
PE3C4486	193	6
PE3C4487	123	37
PE3C4488	123	41
PE3C4489	147	32
PE3C4490	204	77
PE3C4535	176	37
PE3C4680	100	65
PE3C4680-12	350	34
PE3C4680-24	350	35
PE3C4680-48	350	36
PE3C4750	152	62
PE3C4801	203	48
PE3C4807	135	63
PE3C4844	113	71
PE3C4845	117	63
PE3C4846	117	60
PE3C4848	115	25
PE3C4849	118	86
PE3C4850	114	85
PE3C4851	113	82
PE3C4852	113	77
PE3C4853	114	90
PE3C4854	114	5
PE3C4855	117	72
PE3C4856	116	41
PE3C4857	115	11
PE3C4858	117	76
PE3C4859	116	47
PE3C4860	114	98
PE3C4861	117	69
PE3C4862	116	35
PE3C4863	115	21
PE3C4864	118	83
PE3C4865	116	57
PE3C4866	115	16
PE3C4867	117	78
PE3C4868	116	52
PE3C4869	115	18
PE3C4870	118	80
PE3C4871	116	54
PE3C4872	113	75
PE3C4873	117	66
PE3C4874	117	61
PE3C4875	115	29
PE3C4876	118	88
PE3C4877	114	88
PE3C4878	113	83
PE3C4879	113	81
PE3C4880	114	92
PE3C4881	114	9
PE3C4882	117	74
PE3C4883	116	45
PE3C4884	115	15
PE3C4885	117	77
PE3C4886	116	51
PE3C4887	114	3
PE3C4888	117	70
PE3C4889	116	39
PE3C4890	115	23
PE3C4891	118	84
PE3C4892	117	59
PE3C4893	115	17
PE3C4894	117	79
PE3C4895	116	53
PE3C4896	115	19
PE3C4897	118	81
PE3C4898	116	55
PE3C4899	113	70
PE3C4900	117	62
PE3C4901	115	24
PE3C4902	118	85
PE3C4903	114	84
PE3C4904	113	76
PE3C4905	114	89
PE3C4906	114	4
PE3C4907	117	71
PE3C4908	116	40
PE3C4909	115	10
PE3C4910	117	75
PE3C4911	116	46
PE3C4912	114	97
PE3C4913	117	68
PE3C4914	116	34
PE3C4915	115	20
PE3C4916	118	82
PE3C4917	116	56
PE3C4918	114	93
PE3C4919	117	67
PE3C4920	115	30
PE3C4921	113	74
PE3C4922	117	65
PE3C4923	115	28
PE3C4924	114	87
PE3C4925	113	80
PE3C4926	116	44
PE3C4927	114	8
PE3C4928	116	50
PE3C4929	115	14
PE3C4930	116	38
PE3C4931	114	2
PE3C4934	115	33
PE3C4935	114	96
PE3C4936	113	72
PE3C4937	117	64
PE3C4938	115	26
PE3C4939	114	86
PE3C4940	113	78
PE3C4941	116	42
PE3C4942	114	6
PE3C4943	116	48
PE3C4944	116	36
PE3C4945	114	99

Model No.	Page	C/R
PE3C4948	115	31
PE3C4949	114	94
PE3C4950	113	73
PE3C4951	115	27
PE3C4952	118	87
PE3C4953	113	79
PE3C4954	114	91
PE3C4955	114	7
PE3C4956	116	43
PE3C4957	115	13
PE3C4958	116	49
PE3C4959	114	1
PE3C4960	116	37
PE3C4961	115	22
PE3C4962	117	58
PE3C4963	114	95
PE3C4964	115	32
PE3C4968	175	11
PE3C4969	202	28
PE3C5030	156	46
PE3C5233	163	98
PE3C5241	166	30
PE3C5242	172	25
PE3C5244	184	68
PE3C5246	169	20
PE3C5247	192	74
PE3C5248	183	20
PE3C5249	206	36
PE3C5250	209	33
PE3C5251	212	77
PE3C5252	208	88
PE3C5253	211	72
PE3C5254	210	45
PE3C5255	137	21
PE3C5256	155	33
PE3C5257	142	91
PE3C5258	176	39
PE3C5259	177	84
PE3C5260	211	64
PE3C5261	186	17
PE3C5262	186	24
PE3C5263	187	31
PE3C5264	193	12
PE3C5265	193	15
PE3C5266	194	18
PE3C5267	148	46
PE3C5268	149	72
PE3C5269	149	75
PE3C5270	156	49
PE3C5271	156	52
PE3C5272	156	53
PE3C5273	146	98
PE3C5274	155	39
PE3C5275	147	15
PE3C5276	155	42
PE3C5277	147	26
PE3C5278	156	45
PE3C5279	152	57
PE3C5280	152	61
PE3C5281	152	59
PE3C5282	152	63
PE3C5283	152	68
PE3C5284	152	67
PE3C5285	139	3
PE3C5286	151	37
PE3C5287	150	3
PE3C5480	178	89
PE3C5491	215	44
PE3C5570	219	29
PE3C5767	172	24
PE3C5833	96	29
PE3C5834	96	4
PE3C5835	97	18
PE3C5836	96	40
PE3C5837	96	41
PE3C5838	96	42
PE3C5839	96	43
PE3C5840	96	21
PE3C5841	96	3
PE3C5842	96	22
PE3C5843	96	23
PE3C5844	96	24
PE3C5845	96	25
PE3C5846	96	15
PE3C5847	96	2
PE3C5848	96	17
PE3C5849	96	18
PE3C5850	96	19
PE3C5851	96	20
PE3C5852	96	14
PE3C5853	96	31
PE3C5854	96	6
PE3C5855	96	45
PE3C5856	96	54
PE3C5857	96	55
PE3C5858	96	56
PE3C5859	96	34
PE3C5860	96	10
PE3C5861	96	48
PE3C5862	96	83
PE3C5863	96	63
PE3C5864	96	69
PE3C5865	96	32
PE3C5866	96	8
PE3C5867	96	46
PE3C5868	96	81
PE3C5869	96	61
PE3C5870	96	64
PE3C5871	96	33
PE3C5872	96	9
PE3C5873	96	47
PE3C5874	96	82
PE3C5875	96	62
PE3C5876	96	68
PE3C5877	96	67
PE3C5878	96	37
PE3C5879	96	13
PE3C5880	96	51
PE3C5881	96	86
PE3C5882	96	66
PE3C5883	96	72
PE3C5884	96	35
PE3C5885	96	11
PE3C5886	96	49
PE3C5887	96	84
PE3C5888	96	70
PE3C5889	96	36

Model No.	Page	C/R
PE3C5890	96	12
PE3C5891	96	50
PE3C5892	96	85
PE3C5893	96	65
PE3C5894	96	71
PE3C5895	96	73
PE3C5950	96	16
PE3C5980	180	39
PE3C5984	99	54
PE3C5998	97	6
PE3C6069	132	92
PE3C6086	219	45
PE3C6172	103	32
PE3C6173	103	36
PE3C6174	104	68
PE3C6175	104	52
PE3C6176	104	64
PE3C6177	106	16
PE3C6178	104	53
PE3C6179	104	54
PE3C6180	104	65
PE3C6181	109	64
PE3C6182	110	4
PE3C6183	111	38
PE3C6184	105	73
PE3C6185	107	25
PE3C6186	105	74
PE3C6187	103	39
PE3C6188	109	90
PE3C6189	111	36
PE3C6190	110	19
PE3C6191	110	20
PE3C6192	110	11
PE3C6193	110	16
PE3C6194	111	26
PE3C6195	111	28
PE3C6196	112	42
PE3C6197	112	43
PE3C6198	111	40
PE3C6199	112	41
PE3C6200	141	51
PE3C6201	142	96
PE3C6202	137	33
PE3C6203	151	32
PE3C6204	151	40
PE3C6205	140	11
PE3C6206	150	11
PE3C6207	167	53
PE3C6208	183	26
PE3C6209	152	58
PE3C6210	169	27
PE3C6211	152	60
PE3C6212	147	18
PE3C6213	146	2
PE3C6214	155	40
PE3C6215	154	6
PE3C6216	156	43
PE3C6217	154	8
PE3C6218	103	41
PE3C6219	106	98
PE3C6220	105	94
PE3C6221	105	89
PE3C6222	107	30
PE3C6223	105	90
PE3C6224	112	49
PE3C6225	105	95
PE3C6226	106	99
PE3C6227	106	20
PE3C6228	105	92
PE3C6229	104	69
PE3C6230	105	83
PE3C6231	107	29
PE3C6232	105	84
PE3C6233	107	38
PE3C6234	103	42
PE3C6235	108	41
PE3C6236	105	80
PE3C6237	107	28
PE3C6238	105	81
PE3C6239	107	32
PE3C6240	108	43
PE3C6241	108	46
PE3C6242	107	31
PE3C6243	105	93
PE3C6244	112	51
PE3C6245	107	33
PE3C6246	106	5
PE3C6247	106	6
PE3C6248	106	8
PE3C6249	107	34
PE3C6250	106	9
PE3C6251	111	30
PE3C6252	112	44
PE3C6253	214	28
PE3C6254	154	10
PE3C6255	157	62
PE3C6256	149	88
PE3C6257	152	70
PE3C6258	179	17
PE3C6259	187	42
PE3C6260	112	54
PE3C6261	106	11
PE3C6262	107	35
PE3C6263	106	12
PE3C6264	108	51
PE3C6331	107	36
PE3C6332	107	21
PE3C6333	107	39
PE3C6336	108	44
PE3C6337	108	47
PE3C6338	108	52
PE3C6339	106	17
PE3C6340	107	26
PE3C6341	109	65
PE3C6342	110	12
PE3C6343	110	17
PE3C6344	111	31
PE3C6345	137	34
PE3C6346	140	12
PE3C6347	149	89
PE3C6348	107	37
PE3C6349	107	22
PE3C6350	108	40
PE3C6351	108	45
PE3C6352	108	48
PE3C6353	108	53
PE3C6354	106	18

Model No.	Page	C/R
PE3C6355	107	27
PE3C6356	109	66
PE3C6357	110	13
PE3C6358	110	18
PE3C6359	111	32
PE3C6360	137	35
PE3C6361	140	13
PE3C6362	149	90
PE3C6363	104	55
PE3C6365	105	75
PE3C6369	110	14
PE3C6370	137	36
PE3C6371	137	37
PE3C6372	140	14
PE3C6373	150	12
PE3C6374	137	38
PE3C6375	140	15
PE3C6376	150	13
PE3C6378	153	91
PE3C6379	153	92
PE3C6380	104	56
PE3C6381	105	85
PE3C6382	105	91
PE3C6383	112	46
PE3C6384	112	50
PE3C6385	137	39
PE3C6437	104	57
PE3C6445	104	58
PE3C6484	97	7
PE3C6485	98	22
PE3C6486	100	68
PE3C6487	97	8
PE3C6488	98	23
PE3C6489	100	69
PE3C6490	97	9
PE3C6491	97	10
PE3C6492	100	70
PE3C6493	100	71
PE3C6498	104	59
PE3C6499	105	96
PE3C6500	105	76
PE3C6501	105	86
PE3C6502	109	67
PE3C6503	110	5
PE3C6504	112	45
PE3C6505	105	97
PE3C6506	105	77
PE3C6507	105	87
PE3C6508	109	68
PE3C6509	110	6
PE3C6510	112	47
PE3C6511	109	69
PE3C6512	105	78
PE3C6513	104	60
PE3C6514	109	70
PE3C6515	105	79
PE3C6516	104	61
PE3C6575	125	76
PE3C6605	104	62
PE3C6631	168	90
PE3C6632	160	34
PE3C6633	159	31
PE3C6634	159	33
PE3C6635	100	76
PE3C6636	100	63
PE3C6637	100	64
PE3C6638	97	15
PE3C6639	97	21
PE3C6640	99	55
PE3C6658	182	12
PE3C6663	119	33
PE3C6665	120	57
PE3C6783	216	65
PE3C6787	197	3
PE3C6788	122	21
PE3C6845	121	72
PE3C6848	216	57
PE3C6914	125	78
PE3C7425	216	66
PE3C7571	184	66
PE3C7572	201	6
PE3C7582	184	75
PE3C7585	128	82
PE3C7587	157	82
PE3C7590	215	46
PE3C7597	210	49
PE3C7602	197	4
PE3C7615	137	22
PE3C7619	215	45
PE3C7629	132	93
PE3C7715	122	20
PE3C7720	113	68
PE3C7803	99	51
PE3C7819	102	12
PE3C7820	102	14
PE3C7821	102	17
PE3C7822	102	19
PE3C7823	103	30
PE3C7824	103	33
PE3C7825	103	34
PE3C7826	104	50
PE3C7827	104	63
PE3C7828	104	66
PE3C7829	104	70
PE3C7830	105	71
PE3C7831	106	14
PE3C7832	106	19
PE3C7833	107	23
PE3C7834	107	24
PE3C7835	108	62
PE3C7836	109	89
PE3C7837	110

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE3CA1130	166	50
PE3M0001	93	5
PE3M0002	93	6
PE3M0003	93	7
PE3M0004	93	8
PE3M0005	93	9
PE3M0006	93	10
PE3M0007	93	11
PE3M0008	93	36
PE3M0009	93	37
PE3M0010	93	38
PE3M0011	93	42
PE3M0012	93	43
PE3M0013	93	44
PE3M0014	93	39
PE3M0015	93	40
PE3M0016	93	41
PE3M0017	93	45
PE3M0018	93	47
PE3M0019	93	49
PE3M0020	93	46
PE3M0021	93	48
PE3M0022	93	50
PE3M0023	94	86
PE3M0024	94	87
PE3M0025	94	89
PE3M0026	94	88
PE3M0027	94	90
PE3M0028	94	21
PE3M0029	93	12
PE3M0030	93	13
PE3M0031	93	14
PE3M0032	93	15
PE3M0033	93	16
PE3M0034	93	17
PE3M0035	93	18
PE3M0036	93	51
PE3M0037	93	52
PE3M0038	93	53
PE3M0039	93	57
PE3M0040	93	58
PE3M0041	93	59
PE3M0042	93	54
PE3M0043	93	55
PE3M0044	93	56
PE3M0045	93	60
PE3M0046	93	62
PE3M0047	93	64
PE3M0048	93	61
PE3M0049	93	63
PE3M0050	93	65
PE3M0051	94	91
PE3M0052	94	92
PE3M0053	94	94
PE3M0054	94	93
PE3M0055	94	95
PE3M0056	94	22
PE3M0057	93	29
PE3M0058	93	30
PE3M0059	93	31
PE3M0060	93	32
PE3M0061	93	33
PE3M0062	93	34
PE3M0063	93	35
PE3M0064	93	66
PE3M0065	93	67
PE3M0066	93	68
PE3M0067	93	72
PE3M0068	93	73
PE3M0069	94	74
PE3M0070	93	69
PE3M0071	93	70
PE3M0072	93	71
PE3M0073	94	75
PE3M0074	94	77
PE3M0075	94	79
PE3M0076	94	76
PE3M0077	94	78
PE3M0078	94	80
PE3M0079	94	15
PE3M0080	94	16
PE3M0081	94	18
PE3M0082	94	17
PE3M0083	94	19
PE3M0084	94	25
PE3M0085	93	19
PE3M0086	93	20
PE3M0087	93	21
PE3M0088	93	22
PE3M0089	93	23
PE3M0090	94	96
PE3M0091	94	97
PE3M0092	94	98
PE3M0093	94	1
PE3M0094	94	2
PE3M0095	94	4
PE3M0096	94	99
PE3M0097	94	3
PE3M0098	94	5
PE3M0099	94	23
PE3M0100	93	24
PE3M0101	93	25
PE3M0102	93	26
PE3M0103	93	27
PE3M0104	93	28
PE3M0105	94	6
PE3M0106	94	7
PE3M0107	94	8
PE3M0108	94	10
PE3M0109	94	11
PE3M0110	94	13
PE3M0111	94	9
PE3M0112	94	12
PE3M0113	94	14
PE3M0114	94	24
PE3M0115	93	1
PE3M0116	93	2
PE3M0117	93	3
PE3M0118	93	4
PE3M0119	94	81
PE3M0120	94	82
PE3M0121	94	84
PE3M0122	94	83
PE3M0123	94	85
PE3M0124	94	20
PE3M0125	94	47
PE3M0126	94	49

Model No.	Page	C/R
PE3M0127	94	50
PE3M0128	94	48
PE3M0129	94	51
PE3M0130	94	53
PE3M0131	94	52
PE3M0132	94	44
PE3M0133	94	46
PE3M0134	94	45
PE3M0135	94	69
PE3M0136	94	70
PE3M0137	94	67
PE3M0138	94	72
PE3M0139	94	76
PE3M0140	94	74
PE3M0141	94	61
PE3M0142	94	65
PE3M0143	94	63
PE3M0144	94	71
PE3M0145	94	68
PE3M0146	94	73
PE3M0147	94	77
PE3M0148	94	75
PE3M0149	94	62
PE3M0150	94	66
PE3M0151	94	64
PE3M0152	94	57
PE3M0153	94	58
PE3M0154	94	60
PE3M0155	94	59
PE3M0156	94	54
PE3M0157	94	56
PE3M0158	94	55
PE3M0159	95	19
PE3M0160	95	21
PE3M0161	95	20
PE3M0162	95	16
PE3M0163	95	18
PE3M0164	95	17
PE3M0165	95	30
PE3M0166	95	29
PE3M0167	95	26
PE3M0168	95	28
PE3M0169	95	27
PE3M0170	95	25
PE3M0171	95	22
PE3M0172	95	24
PE3M0173	95	23
PE3M0174	94	26
PE3M0175	94	28
PE3M0176	94	27
PE3M0177	94	31
PE3M0178	94	30
PE3M0179	94	29
PE3M0180	95	81
PE3M0181	95	83
PE3M0182	95	82
PE3M0183	95	84
PE3M0184	95	86
PE3M0185	95	85
PE3M0186	94	78
PE3M0187	94	80
PE3M0188	94	79
PE3M0189	95	98
PE3M0190	95	97
PE3M0191	95	99
PE3M0192	95	2
PE3M0193	95	1
PE3M0194	95	94
PE3M0195	95	96
PE3M0196	95	95
PE3M0197	95	90
PE3M0198	95	91
PE3M0199	95	93
PE3M0200	95	92
PE3M0201	95	87
PE3M0202	95	89
PE3M0203	95	88
PE3M0204	95	34
PE3M0205	95	36
PE3M0206	95	35
PE3M0207	95	31
PE3M0208	95	33
PE3M0209	95	32
PE3M0210	95	45
PE3M0211	95	44
PE3M0212	95	41
PE3M0213	95	43
PE3M0214	95	42
PE3M0215	95	40
PE3M0216	95	37
PE3M0217	95	39
PE3M0218	95	38
PE3M0219	94	32
PE3M0220	94	34
PE3M0221	94	33
PE3M0222	94	37
PE3M0223	94	36
PE3M0224	94	35
PE3M0225	95	6
PE3M0226	95	7
PE3M0227	95	8
PE3M0228	95	9
PE3M0229	95	3
PE3M0230	95	5
PE3M0231	95	4
PE3M0232	95	13
PE3M0233	95	14
PE3M0234	95	15
PE3M0235	95	10
PE3M0236	95	12
PE3M0237	95	11
PE3M0238	95	49
PE3M0239	95	50
PE3M0240	95	46
PE3M0241	95	48
PE3M0242	95	47
PE3M0243	95	54
PE3M0244	95	51
PE3M0245	95	53
PE3M0246	95	52
PE3M0247	94	38
PE3M0248	94	40
PE3M0249	94	39
PE3M0250	94	43
PE3M0251	94	42
PE3M0252	94	41
PE3TC0101	166	45

Model No.	Page	C/R
PE3TC0101-24	353	77
PE3TC0102	171	86
PE3TC0102-24	353	75
PE3TC0103	137	28
PE3TC0103-24	353	73
PE3TC0104	141	48
PE3TC0104-24	353	72
PE3TC0105	163	46
PE3TC0105-24	353	74
PE3TC0201	166	46
PE3TC0201-24	353	78
PE3TC0202	171	87
PE3TC0202-24	353	76
PE3TC0301	166	47
PE3TC0301-24	353	81
PE3TC0302	137	29
PE3TC0302-24	353	79
PE3TC0303	163	47
PE3TC0303-24	353	80
PE3TC0401	166	48
PE3TC0401-24	353	82
PE3TC0500	99	52
PE3TC0500-24	351	63
PE3TC0500-48	351	63
PE3TC0600	100	59
PE3TC0600-24	352	64
PE3TC0600-48	352	64
PE3TC0650	100	61
PE3TC0660	214	37
PE3TC0670	214	38
PE3TC0700	100	57
PE3TC0700-24	352	65
PE3TC0700-48	352	65
PE3TC0800	97	11
PE3TC0800-24	352	66
PE3TC0800-48	352	66
PE3TC0800-500CM	352	68
PE3TC0900	97	20
PE3TC0900-24	352	67
PE3TC0900-48	352	67
PE3TC0950	98	25
PE3TC0960	214	35
PE3TC0970	214	36
PE3TC1000	97	19
PE3TC1000-24	352	69
PE3TC1000-48	352	69
PE3TC1100	120	35
PE3TC1101	121	93
PE3TC1102	137	20
PE3TC1103	141	45
PE3TC1200	220	58
PE3TC1201	220	65
PE3TC1202	218	17
PE3TC1203	218	28
PE3TC1204	220	57
PE3TC1205	220	55
PE3TC1206	219	31
PE3TC1220	97	4
PE3TC1220-6	352	70
PE3TC1220-12	352	70
PE3TC1221	97	5
PE3TC1221-6	352	71
PE3TC1221-12	352	71
PE3VNA1801	168	91
PE3VNA1801-24	351	62
PE3VNA1802	171	7
PE3VNA1802-24	351	61
PE3VNA1803	139	75
PE3VNA1803-24	351	60
PE3VNA1804	142	75
PE3VNA1804-24	351	59
PE3VNA1805	146	9
PE3VNA1806	147	25
PE3VNA2603	101	91
PE3VNA2603-24	351	58
PE3VNA2603	354	91
PE3VNA2604	101	1
PE3VNA2604-24	351	57
PE3VNA2604	354	92
PE3VNA2605	100	77
PE3VNA2605-24	351	55
PE3VNA2605	354	93
PE3VNA2606	101	83
PE3VNA2606-24	351	53
PE3VNA2606	354	94
PE3VNA2607	215	42
PE3VNA2610	215	41
PE3VNA4001	100	78
PE3VNA4001-24	351	56
PE3VNA4001	354	95
PE3VNA4002	101	84
PE3VNA4002-24	351	54
PE3VNA4002	354	96
PE3VNA4004	99	56
PE3VNA4004-24	351	52
PE3VNA4004	354	97
PE3VNA4005	100	60
PE3VNA4005-24	351	51
PE3VNA4005	354	98
PE3VNA4007	214	39
PE3VNA4008	214	40
PE3W00013	148	44
PE3W00020	152	65
PE3W00032	122	22
PE3W00037	210	42
PE3W00099	131	62
PE3W00109	138	43
PE3W00135	193	97
PE3W00140	144	60
PE3W00148	123	28
PE3W00169	187	37
PE3W00177	164	83
PE3W00245	190	38
PE3W00250	164	86
PE3W00288	217	88
PE3W00305	159	21
PE3W00314	130	29
PE3W00365	167	73
PE3W00393	120	53
PE3W00415	156	51
PE3W00416	174	92
PE3W00417	138	61
PE3W00430	139	98
PE3W00447	150	93
PE3W00504	164	81
PE3W00507	164	80
PE3W00572	206	32

Model No.	Page	C/R
PE3W00597	198	33
PE3W00676	141	44
PE3W00780	208	2
PE3W00808	207	67
PE3W00825	190	37
PE3W00832	163	40
PE3W00852	182	92
PE3W00906	173	61
PE3W00921	182	90
PE3W00934	191	55
PE3W01041	119	32
PE3W01114	181	84
PE3W01127	139	99
PE3W01283	175	15
PE3W01300	131	59
PE3W01357	119	34
PE3W01379	212	81
PE3W01570	131	52
PE3W01582	166	39
PE3W01626	163	45
PE3W01634	125	81
PE3W01739	185	5
PE3W01818	215	43
PE3W01959	205	13
PE3W01992	121	74
PE3W02012	143	28
PE3W02172	178	90
PE3W02209	127	71
PE3W02215	149	71
PE3W02336	179	36
PE3W02356	148	67
PE3W02390	187	44
PE3W02458	167	80
PE3W02466	171	79
PE3W02547	142	88
PE3W02744	181	83
PE3W02882	181	82
PE3W02943	128	80
PE3W02965	193	96
PE3W02976	153	96
PE3W02993	169	38
PE3W02994	184	65
PE3W03014	174	94
PE3W03030	197	6
PE3W03032	188	91
PE3W03076	159	28
PE3W03154	135	58
PE3W03175	211	65
PE3W03271	110	10
PE3W03310	131	50
PE3W03353	166	44
PE3W03361	128	84
PE3W03365	155	31
PE3W03377	125	80
PE3W03391	129	7
PE3W03417	211	66
PE3W03496	113	69
PE3W03503	159	14
PE3W03530	108	59
PE3W03550	100	62
PE3W03670	123	30
PE3W03751	169	39
PE3W03763	185	3
PE3W03777	202	27
PE3W03803	143	33
PE3W03859	188	90
PE3W03922	101	98
PE3W03981	189	3
PE3W03991	151	35
PE3W04028	206	24
PE3W04051	146	96
PE3W04152	198	39
PE3W04161	196	65
PE3W04200	198	40
PE3W04201	205	14
PE3W04229	146	13
PE3W04230	145	81
PE3W04293	210	57
PE3W04417	191	66
PE3W04423	154	7
PE3W04442	169	45
PE3W04458	176	31
PE3W04476	174	93
PE3W04513	198	32
PE3W04530	220	66
PE3W04585	145	72
PE3W04619	158	96
PE3W04623	194	30
PE3W04625	194	31
PE3W04763	156	47
PE3W04802	202	29
PE3W04854	124	64
PE3W04971	171	82
PE3W04994	203	67
PE3W05056	201	24
PE3W05081	129	22
PE3W05106	185	2
PE3W05115	202	42
PE3W05192	97	1
PE3W05224	178	98
PE3W05242	206	27
PE3W05274	175	14
PE3W05298	182	91
PE3W05361	174	95
PE3W05401	148	68
PE3W05425	211	67
PE3W05426	200	3
PE3W05453	153	90
PE3W05481	202	30
PE3W05483	136	91
PE3W05498	201	5
PE3W05518	204	81
PE3W05541	211	70
PE3W05557	195	49
PE3W05610	212	84
PE3W05630	156	44
PE3W05645	131	51
PE3W05651	148	69
PE3W05673	201	23
PE3W05692	202	26
PE3W05738	206	26
PE3W05740	201	25
PE3W05752	211	71
PE3W05762	212	83
PE3W05881	123	23
PE3W05930	195	48
PE3W05962	192	69

Model No.	Page	C/R
PE3W06017	202	45
PE3W06018	202	43
PE3W06020	221	95
PE3W06055	190	28
PE3W06085	187	45
PE3W06095	149	91
PE3W06096	151	34
PE3W06234	201	21
PE3W06305	125	79
PE3W06365	145	74
PE3W06405	155	41
PE3W06410	175	23
PE3W06417	147	16
PE3W06425	182	15
PE3W06441	151	38
PE3W06444	218	10
PE3W06468	130	49
PE3W06580	208	5
PE3W06649	124	66
PE3W06660	182	16
PE3W06682	158	85
PE3W06701	175	12
PE3W06709	210	44
PE3W06717	202	44
PE3W06829	186	22
PE3W06862	123	25
PE3W06863	140	21
PE3W06905	197	5
PE3W06981	117	73
PE3W07034	218	9
PE3W07044	201	9
PE3W07068	136	93
PE3W07094	123	27
PE3W07181	177	88
PE3W07225	173	70
PE3W07264	149	76
PE3W07265	206	25
PE3W07334	192	73
PE3W07396	131	60
PE3W07452	162	19
PE3W07480	124	65
PE3W07481	96	7
PE3W07489	96	91
PE3W07491	100	79
PE3W07493	174	99
PE3W07532	134	34
PE3W07591	136	88
PE3W07602	219	46
PE3W07619	157	64
PE3W07646	210	46
PE3W07647	210	50
PE3W07649	209	31
PE3W07653	136	89
PE3W07670	192	70
PE3W07719	123	29
PE3W07758	212	82
PE3W07894	136	92
PE3W07895	98	24
PE3W07899	141	71
PE3W07964	131	61
PE3W08014	99	50
PE3W08023	203	51
PE3W10097	121	90
PE3W10654	181	81
PE3W10767	211	68
PE4000	274	23
PE4000-SF	Web	
PE4001	271	48
PE4002	269	66
PE4003	273	83
PE4004	270	1
PE4005	260	71
PE4006	269	91
PE4007	269	82
PE4008	271	44
PE4009	249	25
PE4010	249	28
PE4011	Web	
PE4012	Web	
PE4013	249	17
PE4014	249	15
PE4015	247	57
PE4016	284	61
PE4017	247	44
PE4018	284	66
PE4019	290	78
PE4020	290	69
PE4021	285	3
PE4022	247	37
PE4023	247	38
PE4024	271	59
PE4025	269	58
PE4026	269	64
PE4027	270	35
PE4028	Web	
PE4029	271	69
PE4030	271	70
PE4031	272	19
PE4032	272	20
PE4033	273	93
PE4034	273	94
PE4035	270	2
PE4036	270	6
PE4037	271	62
PE4038	271	63
PE4039	271	91
PE4040	271	92
PE4041	261	81
PE4042	Web	
PE4043	247	56
PE4044	279	80
PE4045	277	33
PE4046	286	20
PE4047	261	1
PE4048	249	20
PE4049	279	89
PE4051	278	44
PE4052	248	69
PE4053	286	49
PE4054	249	29
PE4055	249	22
PE4056	248	87
PE4057	248	86
PE4058	263	75
PE4059	264	47
PE4060	263	72
PE4061		

Model No.	Page	C/R
PE4062	261	76
PE4063	288	4
PE4064	288	8
PE4064SP	288	7
PE4065	288	2
PE4066	Web	
PE4067	286	14
PE4068	287	65
PE4069	290	76
PE4070	248	88
PE4071	286	36
PE4072	263	73
PE4073	290	77
PE4074	279	81
PE4075	257	64
PE4076	257	57
PE4077	249	19
PE4078	249	3
PE4079	248	90
PE4080	277	34
PE4081	261	77
PE4082	248	65
PE4083	271	56
PE4084	247	35
PE4085	Web	
PE4088	286	13
PE4089	300	6
PE4091	249	16
PE4092	248	78
PE4093	257	63
PE4094	279	96
PE4095	280	7
PE4096	278	52
PE4097	278	63
PE4098	257	58
PE4099	274	27
PE4100	268	35
PE4101	273	53
PE4102	Web	
PE4104	299	2
PE4105	300	4
PE4106	249	5
PE4107	280	16
PE4108	270	36
PE4109	247	40
PE4110	297	45
PE4111	274	26
PE4112	270	98
PE4113	263	5
PE4114	263	11
PE4115	271	85
PE4116	271	88
PE4117	272	12
PE4118	Web	
PE4119	272	39
PE4120	Web	
PE4121	273	96
PE4122	Web	
PE4123	274	42
PE4124	Web	
PE4125	270	19
PE4126	270	30
PE4127	270	20
PE4128	273	87
PE4128-SF	273	88
PE4129	260	72
PE4130	262	68
PE4131	262	24
PE4132	261	79
PE4133	260	64
PE4134	263	76
PE4135	262	33
PE4136	262	32
PE4137	264	39
PE4138	262	67
PE4139	264	37
PE4140	261	9
PE4141	264	46
PE4142	286	10
PE4143	286	9
PE4144	287	61
PE4145	287	60
PE4146	286	48
PE4147	Web	
PE4148	287	94
PE4149	287	80
PE4150	287	79
PE4151	287	90
PE4152	287	83
PE4153	287	89
PE4154	286	15
PE4155	287	64
PE4156	286	35
PE4157	Web	
PE4158	297	57
PE4159	278	45
PE4160	279	90
PE4161	296	39
PE4162	298	62
PE4163	297	43
PE4164	298	67
PE4165	Web	
PE4166	Web	
PE4167	278	70
PE4168	297	49
PE4169	298	73
PE4170	278	69
PE4171	280	17
PE4172	297	48
PE4173	298	74
PE4174	278	60
PE4175	279	4
PE4176	298	68
PE4177	278	74
PE4178	280	20
PE4179	297	50
PE4180	298	75
PE4181	257	71
PE4182	254	81
PE4183	254	95
PE4184	282	17
PE4186	274	29
PE4187	Web	
PE4188	272	42
PE4189	273	59
PE4189-SF	Web	
PE4190	272	15

Model No.	Page	C/R
PE4191	263	86
PE4192	255	5
PE4193	257	84
PE4194	268	40
PE4195	248	77
PE4196	273	91
PE4197	273	92
PE4198	254	82
PE4199	282	18
PE4200	277	31
PE4201	279	77
PE4202	279	78
PE4203	296	33
PE4204	248	81
PE4205	248	82
PE4206	247	33
PE4207	247	34
PE4208	249	10
PE4209	249	9
PE4210	247	50
PE4211	248	64
PE4212	248	85
PE4213	270	3
PE4214	269	59
PE4215	269	83
PE4217	274	20
PE4218	274	25
PE4219	272	52
PE4220	Web	
PE4221	261	73
PE4222	Web	
PE4223	263	10
PE4224	261	75
PE4225	257	70
PE4226	257	67
PE4227	257	68
PE4228	258	91
PE4229	254	91
PE4229-401	254	92
PE4230	254	89
PE4231	268	28
PE4232	268	27
PE4233	254	78
PE4234	299	93
PE4235	299	95
PE4236	299	92
PE4237	299	94
PE4238	299	98
PE4239	268	47
PE4240	251	99
PE4241	251	8
PE4242	251	79
PE4243	251	77
PE4244	251	86
PE4245	278	49
PE4246	279	94
PE4247	247	49
PE4248	296	34
PE4249	297	58
PE4250	277	32
PE4251	296	40
PE4252	Web	
PE4254	298	66
PE4255	297	47
PE4256	298	71
PE4257	296	32
PE4258	297	56
PE4259	297	55
PE4260	278	42
PE4261	278	43
PE4262	279	87
PE4263	279	88
PE4264	296	38
PE4266	298	61
PE4268	Web	
PE4269	278	51
PE4270	279	95
PE4272	297	42
PE4274	298	65
PE4275	298	64
PE4276	278	62
PE4278	279	5
PE4279	279	6
PE4281	297	46
PE4283	298	70
PE4284	279	76
PE4285	280	21
PE4288	277	40
PE4289	Web	
PE4290	296	37
PE4291	297	60
PE4293	298	63
PE4294	269	84
PE4295	290	73
PE4296	271	45
PE4297	263	12
PE4298	248	71
PE4299	257	56
PE4300	274	35
PE4301	300	8
PE4302	286	18
PE4303	286	11
PE4304	287	81
PE4305	288	98
PE4306	288	3
PE4307	248	66
PE4308	248	93
PE4309	249	11
PE4311	257	85
PE4312	257	86
PE4313	258	88
PE4314	258	89
PE4315	268	46
PE4316	268	34
PE4317	249	30
PE4318	249	18
PE4319	248	98
PE4320	248	70
PE4321	248	83
PE4322	268	32
PE4323	255	98
PE4324	299	99
PE4325	271	74
PE4326	271	79
PE4327	271	50
PE4328	265	57
PE4329	261	3

Model No.	Page	C/R
PE4330	263	74
PE4331	261	78
PE4332	269	62
PE4333	268	36
PE4334	284	63
PE4335	Web	
PE4336	284	68
PE4337	284	69
PE4338	284	71
PE4339	284	72
PE4340	284	67
PE4341	284	74
PE4342	258	9
PE4343	268	41
PE4344	261	5
PE4345	248	76

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE4459	287	72
PE4460	287	66
PE4461	287	62
PE4462	287	68
PE4463	287	63
PE4464	287	84
PE4465	287	91
PE4466	287	87
PE4467	287	82
PE4468	288	5
PE4469	288	99
PE4470	286	44
PE4471	288	12
PE4472	296	35
PE4473	254	84
PE4474	254	85
PE4475	254	79
PE4476	254	80
PE4477	254	86
PE4478	254	87
PE4479	254	83
PE4480	254	90
PE4481	254	93
PE4482	262	43
PE4483	262	44
PE4484	262	45
PE4485	262	46
PE4486	265	65
PE4487	265	59
PE4488	264	38
PE4489	261	21
PE4490	261	19
PE4490BK	261	20
PE4491	262	22
PE4492	265	60
PE4493	257	60
PE4494	257	55
PE4495	257	83
PE4496	268	37
PE4497	268	39
PE4498	268	33
PE4499	268	49
PE4500	268	48
PE4501	268	50
PE4502	295	18
PE4503	296	23
PE4504	295	17
PE4505	296	22
PE4506	296	21
PE4507	295	11
PE4508	295	16
PE4509	295	8
PE4510	295	13
PE4511	295	10
PE4512	295	15
PE4513	295	9
PE4514	295	20
PE4515	Web	
PE4516	295	19
PE4517	251	84
PE4518	251	81
PE4519	Web	
PE4520	267	25
PE4521	258	8
PE4522	278	48
PE4523	277	37
PE4524	277	49
PE4525	270	14
PE4526	Web	
PE4527	274	24
PE4528	273	56
PE4529	272	51
PE4530	273	57
PE4531	270	16
PE4532	273	58
PE4533	274	28
PE4534	272	14
PE4536	273	54
PE4537	274	22
PE4538	274	21
PE4539	274	30
PE4540	274	19
PE4541	270	28
PE4542	272	7
PE4543	272	8
PE4545	274	34
PE4547	273	90
PE4548	273	95
PE4549	273	55
PE4550	261	92
PE4551	255	8
PE4552	255	12
PE4553	255	20
PE4554	255	21
PE4555	256	36
PE4556	256	45
PE4558	279	79
PE4559	255	19
PE4560	256	47
PE4561	256	41
PE4562	256	28
PE4563	255	96
PE4564	255	97
PE4567	243	16
PE4568	244	26
PE4569	244	27
PE4570	244	24
PE4571	244	25
PE4572	245	72
PE4573	245	77
PE4574	245	79
PE4574A	245	80
PE4575	244	58
PE4576	269	86
PE4577	269	87
PE4578	269	73
PE4579	270	37
PE4580	270	41
PE4587	270	10
PE4589	269	85
PE4590	270	9
PE4591	271	66
PE4592	271	89
PE4593	277	36
PE4595	278	47
PE4596	279	92
PE4598	292	26

Model No.	Page	C/R
PE4599	291	6
PE4600	292	24
PE4601	291	8
PE4602	291	11
PE4603	291	7
PE4604	292	25
PE4605	292	31
PE4607	292	30
PE4608	292	33
PE4609	292	29
PE4610	292	32
PE4611	292	36
PE4613	292	35
PE4615	292	34
PE4616	292	38
PE4617	293	56
PE4618	293	59
PE4619	292	51
PE4620	292	50
PE4621	292	53
PE4622	293	60
PE4623	292	55
PE4624	292	52
PE4625	292	28
PE4626	292	49
PE4627	292	27
PE4628	293	61
PE4630	293	57
PE4631	293	58
PE4632	248	1
PE4633	292	20
PE4634	292	23
PE4637	292	41
PE4638	292	47
PE4639	292	40
PE4640	292	46
PE4641	292	43
PE4642	292	45
PE4643	247	53
PE4644	259	17
PE4645	262	69
PE4646	262	70
PE4647	261	98
PE4648	286	40
PE4649	286	42
PE4650	247	62
PE4651	247	63
PE4652	263	92
PE4653	263	93
PE4654	264	30
PE4655	264	32
PE4656	295	14
PE4657	257	62
PE4658	297	59
PE4659	288	18
PE4660	288	26
PE4661	288	27
PE4662	288	19
PE4663	288	28
PE4664	288	29
PE4665	288	20
PE4666	288	30
PE4667	288	16
PE4668	288	24
PE4669	288	17
PE4670	288	14
PE4671	288	31
PE4672	288	15
PE4673	288	32
PE4674	288	13
PE4676	289	36
PE4677	289	39
PE4678	289	40
PE4679	289	37
PE4680	289	35
PE4681	289	38
PE4682	289	34
PE4683	289	44
PE4684	289	46
PE4685	289	52
PE4686	289	53
PE4687	289	54
PE4688	289	47
PE4689	289	45
PE4690	289	51
PE4691	289	43
PE4692	289	41
PE4693	289	42
PE4694	289	59
PE4695	289	61
PE4696	289	61
PE4699	289	58
PE4700	289	60
PE4701	289	57
PE4702	289	55
PE4703	289	56
PE4704	289	67
PE4705	289	68
PE4706	289	66
PE4708	289	33
PE4709	257	66
PE4710	257	65
PE4711	249	34
PE4712	250	38
PE4713	250	39
PE4714	249	35
PE4715	250	40
PE4716	250	41
PE4717	250	36
PE4718	250	42
PE4719	249	32
PE4720	250	37
PE4721	249	33
PE4722	249	31
PE4727	250	45
PE4728	250	46
PE4729	250	48
PE4730	250	49
PE4732	250	44
PE4733	250	47
PE4735	250	54
PE4736	250	55
PE4737	250	58
PE4738	250	59
PE4739	250	60
PE4741	250	52
PE4742	250	56

Model No.	Page	C/R
PE4743	250	53
PE4744	250	50
PE4745	250	51
PE4746	250	63
PE4747	250	66
PE4748	250	67
PE4749	250	64
PE4751	250	62
PE4752	250	65
PE4755	250	61
PE4756	250	71
PE4757	250	69
PE4758	250	68
PE4759	250	73
PE4762	250	43
PE4763	250	72
PE4764	250	70
PE4766	275	45
PE4767	275	51
PE4768	275	57
PE4769	275	52
PE4770	274	43
PE4771	275	49
PE4772	275	55
PE4773	274	44
PE4775	275	56
PE4777	275	46
PE4780	275	59
PE4782	275	68
PE4784	275	58
PE4785	275	60
PE4786	275	67
PE4788	275	61
PE4790	275	65
PE4791	275	66
PE4792	275	70
PE4793	275	76
PE4794	275	83
PE4795	275	77
PE4797	275	73
PE4798	275	81
PE4799	275	74
PE4800	252	9
PE4801	252	10
PE4804	252	13
PE4807	252	11
PE4808	252	15
PE4812	252	17
PE4815	252	16
PE4816	252	14
PE4838	252	12
PE4850	275	69
PE4851	275	82
PE4852	275	79
PE4853	275	80
PE4854	275	88
PE4855	276	93
PE4856	276	99
PE4857	276	94
PE4858	275	86
PE4859	276	89
PE4860	276	97
PE4861	275	87
PE4862	276	90
PE4863	276	98
PE4864	276	95
PE4865	276	96
PE4866	276	92
PE4867	276	4
PE4868	276	2
PE4869	275	85
PE4870	276	6
PE4871	276	3
PE4872	276	1
PE4874	275	84
PE4875	276	7
PE4876	255	17
PE4877	256	25
PE4878	255	13
PE4879	255	22
PE4880	255	16
PE4881	255	15
PE4882	256	24
PE4883	256	23
PE4884	256	29
PE4885	256	30
PE4886	256	39
PE4887	256	38
PE4888	256	40
PE4889	256	35
PE4890	256	44
PE4891	256	43
PE4892	256	32
PE4893	256	31
PE4894	256	42
PE4896	259	35
PE4897	259	36
PE4898	260	43
PE4899	260	44
PE4901	260	48
PE4902	260	49
PE4903	260	55
PE4904	260	54
PE4905	260	42
PE4906	298	69
PE4907	269	97
PE4908	247	61
PE4909	286	38
PE4910	272	11
PE4911	274	33
PE4912	270	13
PE4913	270	12
PE4914	272	31
PE4915	248	96
PE4916	248	97
PE4917	269	93
PE4918	269	92
PE4919	271	52
PE4920	271	51
PE4921	271	81
PE4922	271	80
PE4923	272	33
PE4924	272	32
PE4926	278	53
PE4927	279	97
PE4928	297	41
PE4930	271	84

Model No.	Page	C/R
PE4931	272	35
PE4932	271	55
PE4933	257	59
PE4934	261	6
PE4935	262	31
PE4936	262	50
PE4937	262	51
PE4938	262	27
PE4940	264	25
PE4941	264	26
PE4942	263	4
PE4943	263	99
PE4945	263	89
PE4946	264	27
PE4949	251	90
PE4950	251	76
PE4951	251	74
PE4952	251	80
PE4953	251	75
PE4954	251	78
PE4955	251	89
PE4957	251	87
PE4958	251	91
PE4959	251	88
PE4960	251	93
PE4961	251	94
PE4963	251	92
PE4964	251	95
PE4965	251	97
PE4967	251	5
PE4969	251	6
PE4971	251	1
PE4972	251	2
PE4973	251	3
PE4974	247	60
PE4975	286	37
PE4978	268	30
PE4979	268	29
PE4980	268	31
PE4981	242	58
PE4982	242	59
PE4985	242	62
PE4987	240	14
PE4988	240	15
PE4992	241	34
PE4993	294	97
PE4994	294	98
PE4995	295	99
PE4996	295	1
PE4997	295	4
PE4998	295	6
PE44000	273	4
PE44001	274	7
PE44003	274	14
PE44004	274	17
PE44005	270	22
PE44007	270	24
PE44008	270	25
PE44009	270	27
PE44010	273	3
PE44011	Web	
PE44012	Web	
PE44013	Web	
PE44014	Web	
PE44015	274	40
PE44016	Web	
PE44017	Web	
PE44018	270	21
PE44019	270	23
PE44021	270	26
PE44022	Web	
PE44023	Web	
PE44024	273	70
PE44025	Web	
PE44026	Web	
PE44027	Web	
PE44028	Web	
PE44029	Web	
PE44030	Web	
PE44031	Web	
PE44032	270	17
PE44035	Web	
PE44036	252	19
PE44037	Web	
PE44038	252	18
PE44040	247	30
PE44042	247	31
PE44043	Web	
PE44044	Web	
PE44045	260	63
PE44046	260	65
PE44047	280	10
PE44048	278	66
PE44049	268	44
PE44050	290	70
PE44051	290	74
PE44052	290	71
PE44053	290	75
PE44054	290	72
PE44055	290	80
PE44056	290	81
PE44057	290	82
PE44058	290	83
PE44059	290	84
PE44060	290	85
PE44061	285	4
PE44062	286	29
PE44063	Web	
PE44064	Web	
PE44065	264	49
PE44066	264	50
PE44068	264	52
PE44069	264	48
PE44070	264	45
PE44071	264	42
PE44072	264	43
PE44073	264	44
PE44074	265	61
PE44075	265	63
PE44076	265	62
PE44077	264	41
PE44078	Web	
PE44079	264	40
PE44080	268	45
PE44081	Web	
PE44082	Web	
PE44083	258	11

Model No.	Page	C/R
PE44084	258	12
PE44085	258	10
PE44086	258	14
PE44087	258	13
PE44088	258	7
PE44089	259	16
PE44090	258	6
PE44091	259	18
PE44092	259	15
PE44093	Web	
PE44094	278	67
PE44095	280	11
PE44096	251	85
PE44098	251	98
PE44099	251	96
PE44100	257	73
PE44102	257	72
PE44103	257	74
PE44104	257	69
PE44105	257	70
PE44106	257	77
PE44107	257	79
PE44108	257	80
PE44109	257	78
PE44110	257	81
PE44111	257	76
PE44112	258	87
PE44114	299	97
PE44115	299	96
PE44116	299	1
PE44117	Web	
PE44118	268	42
PE44119	278	59
PE44120	279	3
PE44121	278	73
PE44122	280	19
PE44123	278	68
PE44124	280	15
PE44126	Web	
PE44127	Web	
PE44128	295	7
PE44129	278	58
PE44130	279	2
PE44131	295	3
PE44132	278	55
PE44135	278	57
PE44136	279	1
PE44137	278	56
PE44138	279	99
PE44139	278	71
PE44140	Web	
PE44141	295	5
PE44142	278	72
PE44143	280	18
PE44145	300	9
PE44146	254	75
PE44147	254	74
PE44148	254	73
PE44149	253	72
PE44161	298	79
PE44162	298	83
PE44163	298	76
PE44164	298	80
PE44165	298	78
PE44166	298	82
PE44167	298	77
PE44168	298	81
PE44169	Web	
PE44171	298	85
PE44172	298	84
PE44173	298	88
PE44174	298	86
PE44175	Web	
PE44176	298	87
PE44177	298	89
PE44178	299	91
PE44180	Web	
PE44181	298	90
PE44182	276	11
PE44183	276	12
PE44184	276	8
PE44185	276	9
PE44186	276	15
PE44187	276	16
PE44188	276	13
PE44189	276	14
PE44190	276	19
PE44191	276	20
PE44192	276	17
PE44193	276	18
PE44194	277	26
PE44195	277	27
PE44196	277	24
PE44197	277	25
PE44198	277	23
PE44199	277	29
PE44200	277	28
PE44201	277	21
PE44202	277	22
PE44203	269	77
PE44204	272	4
PE44205	272	5
PE44206	272	2
PE44207	272	3
PE44208	272	6
PE44210	270	11
PE44211	272	45
PE44212	272	46
PE44213	272	44
PE44214	272	47
PE44215	239	67
PE44216	240	74
PE44217	Web	
PE44218	Web	
PE44219	Web	
PE44220	240	73
PE44221	Web	
PE44223	Web	
PE44225	Web	
PE44226	Web	
PE44227	241	23
PE44228	Web	
PE44229	241	40
PE44230	Web	
PE44231	Web	
PE44232	241	21
PE44233	Web	

Model No.	Page	C/R
PE44234	Web	
PE44235	272	10
PE44236	274	41
PE44237	274	36
PE44238	274	37
PE44239	274	38
PE44240	274	32
PE44241	274	31
PE44242	237	4
PE44243	237	5
PE44244	237	2
PE44247	237	8
PE44248	237	9
PE44249	237	6
PE44254	237	11
PE44256	237	12
PE44257	237	10
PE44258	237	14
PE44259	237	13
PE44260	237	16
PE44261	237	15
PE44262	291	99
PE44263	291	1
PE44264	291	2
PE44268	291	5
PE44270	291	3
PE44271	291	4
PE44274	282	4
PE44275	282	7
PE44276	243	14
PE44277	243	15
PE44278	243	13
PE44279	Web	
PE44280	244	37
PE44281	Web	
PE44282	244	36
PE44283	244	52
PE44284	244	57
PE44285	244	53
PE44286	244	59
PE44287	244	60
PE44288	244	51
PE44289	244	49
PE44290	244	50
PE44291	245	74
PE44292	245	73
PE44293	286	31
PE44294	247	52
PE44295	253	71
PE44296	253	70
PE44297	253	69
PE44298	294	91
PE44300	294	93
PE44301	Web	
PE44302	Web	
PE44303	256	37
PE44304	294	95
PE44305	Web	
PE44306	Web	
PE44308	255	9
PE44309	255	6
PE44310	255	7
PE44311	255	10
PE44312	293	65
PE44313	293	71
PE44314	293	74
PE44315	293	68
PE44316	293	70
PE44317	293	64
PE44318	293	73
PE44319	Web	
PE44320	293	77
PE44321	Web	
PE44322	293	76
PE44323	293	78
PE44324	293	83
PE44325	Web	
PE44326	Web	
PE44327	294	85
PE44328	Web	
PE44329	294	86
PE44330	294	87
PE44331	293	79
PE44332	294	84
PE44333	294	88
PE44334	294	90
PE44335	Web	
PE44336	237	22
PE44337	Web	
PE44338	238	26
PE44339	Web	
PE44340	273	82
PE44341	273	84
PE44342	Web	
PE44343	Web	
PE44344	Web	
PE44345	Web	
PE44346	Web	
PE44347	Web	
PE44348	281	52
PE44349	260	66
PE44350	262	64
PE44351	238	39
PE44352	238	40
PE44353	238	37
PE44354	238	38
PE44355	238	42
PE44356	238	43
PE44357	239	55
PE44358	239	56
PE44359	238	50
PE44360	239	57
PE44361	238	47
PE44362	238	48
PE44363	238	45
PE44364	238	46
PE44365	239	53
PE44366	239	54
PE44367	239	51
PE44368	239	52
PE44369	256	48
PE44370	256	49
PE44371	Web	
PE44372	Web	
PE44374	257	52
PE44375	Web	
PE44376	257	54

Model No.	Page	C/R
PE44377	257	53
PE44378	282	21
PE44379	282	10
PE44380	282	22
PE44381	282	11
PE44382	282	13
PE44383	282	16
PE44384	282	26
PE44385	283	30
PE44386	283	31
PE44387	283	35
PE44388	283	39
PE44389	283	40
PE44390	283	44
PE44391	283	38
PE44392	283	51
PE44393	283	50
PE44394	283	57
PE44395	283	55
PE44396	263	98
PE44397	264	36
PE44398	265	64
PE44401	283	27
PE44402	283	28
PE44403	283	36
PE44404	283	37
PE44405	283	45
PE44406	283	46
PE44416	282	12
PE44417	Web	
PE44418	282	23
PE44419	283	29
PE44420	282	24
PE44421	282	25
PE44422	283	32
PE44424	283	33
PE44425	283	34
PE44426	283	41
PE44427	283	47
PE44428	283	42
PE44429	283	43
PE44430	282	19
PE44432	282	20
PE44433	283	54
PE44434	283	56
PE44435	283	60
PE44436	283	52
PE44437	283	53
PE44438	283	58
PE44439	283	59
PE44440	282	14
PE44441	282	15
PE44442	297	52
PE44443	297	51
PE44445	297	53
PE44446	297	54
PE44447	255	1
PE44448	255	99
PE44449	Web	
PE44450	255	3
PE44451	255	2
PE44452	293	72
PE44453	259	40
PE44454	261	95
PE44455	284	73
PE44456	259	39
PE44457	260	46
PE44458	260	52
PE44459	260	51
PE44460	269	74
PE44461	269	78
PE44470	265	66
PE44471	Web	
PE44472	265	67
PE44474	265	68
PE44475	265	71
PE44476	265	72
PE44477	265	70
PE44478	265	69
PE44479	Web	
PE44480	280	36
PE44481	280	35
PE44482	280	25
PE44483	281	57
PE44485	349	23
PE44486	349	22
PE44487	349	21
PE44488	349	20
PE44489	258	94
PE44490	258	93
PE44491	258	98
PE44492	258	2
PE44493	258	3
PE44494	258	4
PE44495	266	88
PE44496	266	86
PE44497	266	98
PE44498	266	97
PE44499	Web	
PE44500	267	9
PE44501	266	84
PE44502	Web	
PE44503	266	83
PE44504	Web	
PE44505	266	94
PE44506	266	92
PE44507	267	6
PE44508	267	7
PE44509	Web	
PE44510	267	4
PE44511	267	11
PE44512	267	5
PE44514	266	85
PE44515	266	95
PE44520	261	80
PE44521	261	93
PE44522	261	94
PE44523	261	96
PE44524	262	37
PE44525	262	39
PE44526	262	40
PE44527	262	41
PE44528	264	21
PE44529	264	17
PE44530	264	18
PE44531	264	22
PE44532	263	79

Model No.	Page	C/R
PE44533	263	80
PE44534	263	81
PE44535	263	82
PE44536	244	23
PE44537	Web	
PE44538	244	22
PE44539	Web	
PE44540	Web	
PE44541	244	40
PE44542	Web	
PE44543	Web	
PE44544	244	55
PE44545	244	54
PE44546	244	56
PE44547	Web	
PE44548	245	66
PE44549	245	68
PE44550	245	67
PE44551	245	69
PE44552	Web	
PE44553	Web	
PE44554	262	25
PE44555	Web	
PE44556	Web	
PE44558	243	12
PE44560	244	48
PE44563	Web	
PE44564	Web	
PE44565	262	62
PE44566	Web	
PE44567	Web	
PE44568	243	11
PE44569	244	34
PE44570	Web	
PE44572	293	62
PE44573	293	63
PE44574	296	25
PE44575	Web	
PE44576	296	24
PE44577	291	10
PE44578	291	9
PE44579	293	75
PE44580	296	30
PE44581	Web	
PE44582	293	67
PE44583	296	29
PE44584	292	22
PE44585	293	80
PE44586	296	31
PE44587	292	44
PE44588	294	96
PE44589	Web	
PE44590	295	2
PE44591	273	60
PE44592	Web	
PE44593	274	39
PE44594	290	88
PE44595	Web	
PE44596	Web	
PE44597	267	13
PE44598	Web	
PE44599	267	16
PE44600	267	20
PE44601	267	18
PE44602	Web	
PE44603	267	19
PE44604	267	21
PE44605	Web	
PE44607	267	22
PE44608	267	23
PE44609	Web	
PE44610	267	24
PE44613	255	18
PE44614	272	9
PE44615	264	35
PE44616	248	95
PE44618	249	12
PE44619	292	39
PE44620	292	48
PE44622	296	28
PE44623	296	27
PE44624	296	26
PE44625	292	21
PE44626	291	13
PE44627	291	14
PE44628	292	17
PE44630	Web	
PE44631	291	12
PE44632	292	15
PE44633	263	8
PE44634	286	30
PE44635	286	54
PE44636	287	67
PE44637	269	75
PE44638	270	43
PE44639	271	71
PE44640	247	51
PE44641	248	73
PE44642	248	89
PE44643	272	21
PE44644	Web	
PE44645	259	37
PE44646A	253	44
PE44646B	253	45
PE44646C	253	46
PE44646D	253	47
PE44646H	253	48
PE44646I	253	49
PE44646K	253	50
PE44646Z	253	51
PE44647A	Web	
PE44647B	Web	
PE44647C	Web	
PE44647D	Web	
PE44647H	Web	
PE44647I	Web	
PE44647K	Web	
PE44647Z	Web	
PE44648A	253	54
PE44648B	253	55
PE44648C	253	56
PE44648D	253	57
PE44648H	253	58
PE44648I	253

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE44649B	252	29
PE44649C	252	30
PE44649D	252	31
PE44649H	252	32
PE44649I	252	33
PE44649K	252	34
PE44649Z	252	35
PE44650A	253	62
PE44650B	253	63
PE44650C	253	64
PE44650D	253	65
PE44650H	253	66
PE44650I	253	67
PE44650Z	253	68
PE44651A	253	36
PE44651B	253	37
PE44651C	253	38
PE44651D	253	39
PE44651H	253	40
PE44651I	253	41
PE44651K	253	42
PE44651Z	253	43
PE44652	292	54
PE44653	262	23
PE44654	286	43
PE44655	282	94
PE44656	245	70
PE44657	Web	
PE44658	249	6
PE44659	288	9
PE44660	256	34
PE44661	256	33
PE44662	260	53
PE44663	260	41
PE44664	275	47
PE44665	275	72
PE44666	275	48
PE44667	Web	
PE44668	269	76
PE44669	271	72
PE44670	288	22
PE44671	289	49
PE44672	288	23
PE44673	289	50
PE44674	248	80
PE44675	262	42
PE44676	Web	
PE44686	292	16
PE44687	292	42
PE44688	292	37
PE44690	270	99
PE44691	269	88
PE44692	271	58
PE44693	271	57
PE44694	271	87
PE44695	271	86
PE44696	272	38
PE44697	272	36
PE44698	256	26
PE44699	260	47
PE44700	261	12
PE44701	261	10
PE44702	262	52
PE44703	262	49
PE44704	263	94
PE44705	263	91
PE44706	264	31
PE44707	264	29
PE44708	286	41
PE44709	286	39
PE44710	287	59
PE44711	287	58
PE44712	287	75
PE44713	287	74
PE44714	287	95
PE44715	287	93
PE44717	245	76
PE44718	254	94
PE44719	290	86
PE44720	249	24
PE44721	265	53
PE44722	265	54
PE44723	275	78
PE44724	275	54
PE44726	260	58
PE44727	262	58
PE44728	243	9
PE44729	260	57
PE44731	262	57
PE44732	243	8
PE44734	244	47
PE44735	260	61
PE44737	262	61
PE44738	243	7
PE44740	244	46
PE44757	269	94
PE44767	Web	
PE44770	Web	
PE44771	Web	
PE44772	Web	
PE44773	Web	
PE44774	Web	
PE44775	281	50
PE44776	281	51
PE44777	280	28
PE44779	281	53
PE44780	281	54
PE44783	237	7
PE44784	260	45
PE44785	282	92
PE44786	282	93
PE44788	261	2
PE44789	263	87
PE44792	277	35
PE44796	240	8
PE44797	240	7
PE44798	241	22
PE44799	237	17
PE44800	238	27
PE44801	240	85
PE44802	238	32
PE44804	286	17
PE44807	263	3
PE44808	269	55
PE44809	260	69
PE44810	285	8
PE44811	287	77

Model No.	Page	C/R
PE44812	286	45
PE44813	263	1
PE44814	271	65
PE44815	285	6
PE44816	262	28
PE44817	270	31
PE44818	278	46
PE44825	260	67
PE44826	269	53
PE44827	272	13
PE44828	290	79
PE44829	Web	
PE44830	256	27
PE44840	280	49
PE44841	Web	
PE44842	284	70
PE44843	248	72
PE44844	262	38
PE44845	Web	
PE44846	286	53
PE44847	288	10
PE44848	280	13
PE44849	280	48
PE44852	260	50
PE44872	297	44
PE44874	259	38
PE44875	279	75
PE44876	279	91
PE44877	264	24
PE44879	280	27
PE44880	280	26
PE44886	248	2
PE44887	249	21
PE44888	249	23
PE44890	249	13
PE44891	249	14
PE44892	288	11
PE44894	287	97
PE44895	294	89
PE44896	257	82
PE44897	287	76
PE44898	287	96
PE44899	287	86
PE44900	287	86
PE44901	288	6
PE44902	289	62
PE44903	289	63
PE44904	241	49
PE44905	241	48
PE44906	Web	
PE44907	281	60
PE44908	282	6
PE44909	281	85
PE44910	280	46
PE44911	282	5
PE44912	281	86
PE44913	282	9
PE44914	282	8
PE44915	282	3
PE44916	281	64
PE44917	282	91
PE44918	281	79
PE44919	281	80
PE44920	281	81
PE44921	281	73
PE44922	281	74
PE44923	281	70
PE44924	281	71
PE44925	281	75
PE44926	281	76
PE44927	281	77
PE44928	281	72
PE44929	Web	
PE44930	281	78
PE44931	281	88
PE44932	281	67
PE44933	281	68
PE44934	281	89
PE44935	281	65
PE44936	280	47
PE44937	280	44
PE44938	281	66
PE44939	282	97
PE44940	280	45
PE44942	280	23
PE44943	280	22
PE44944	280	31
PE44945	281	69
PE44946	280	32
PE44947	280	33
PE44948	281	59
PE44949	281	61
PE44950	281	62
PE44951	281	63
PE44952	280	34
PE44953	281	82
PE44955	280	24
PE44956	281	87
PE44957	280	40
PE44958	280	37
PE44959	280	38
PE44960	280	39
PE44961	281	55
PE44962	Web	
PE44963	281	83
PE44964	281	84
PE44965	280	41
PE44966	280	42
PE44967	280	43
PE44968	258	97
PE44969	258	98
PE44970	258	95
PE44971	258	99
PE44972	258	5
PE44973	258	96
PE44974	258	1
PE44975	275	63
PE44976	260	56
PE44977	279	84
PE44978	267	14
PE44979	244	35
PE44993	243	10
PE44994	244	21
PE44995	Web	
PE44996	270	34
PE44998	273	97
PE45000	245	78

Model No.	Page	C/R
PE45001	243	20
PE45002	261	11
PE45004	276	92
PE45005	237	18
PE45008	275	53
PE45011	242	60
PE45012	275	64
PE45032	238	44
PE45035	258	90
PE45036	262	59
PE45037	243	17
PE45039	273	86
PE45040	269	70
PE45041	270	33
PE45042	269	56
PE45045	247	42
PE45046	244	39
PE45047	264	19
PE45048	270	39
PE45050	256	51
PE45051	256	50
PE45053	274	18
PE45054	Web	
PE45055	273	80
PE45064	249	4
PE45065	286	32
PE45067	273	85
PE45071	267	15
PE45085	265	58
PE45086	294	92
PE45114	247	43
PE45116	292	19
PE45117	292	18
PE45119	277	38
PE45126	281	56
PE45127	281	58
PE45128	282	99
PE45130	288	1
PE45131	249	8
PE45132	287	92
PE45133	264	51
PE45134	272	48
PE45135	270	5
PE45136	272	25
PE45137	271	76
PE45138	272	29
PE45139	270	18
PE45140	269	65
PE45141	272	30
PE45142	269	63
PE45143	287	69
PE45144	271	47
PE45145	269	79
PE45147	280	14
PE45150	248	94
PE45153	284	62
PE45154	Web	
PE45155	279	82
PE45156	279	98
PE45157	280	9
PE45158	278	54
PE45159	278	65
PE45160	Web	
PE45161	286	19
PE45162	284	65
PE45163	Web	
PE45164	300	7
PE45165	276	10
PE45166	237	3
PE45168	255	11
PE45169	255	8
PE45170	238	41
PE45171	238	49
PE45172	263	84
PE45173	263	9
PE45174	286	56
PE45176	253	52
PE45176Z	253	53
PE45177	287	88
PE45180	288	25
PE45181	289	64
PE45182	250	57
PE45183	275	50
PE45185	275	62
PE45186	275	75
PE45189	276	91
PE45190	Web	
PE45193	279	93
PE45195	284	64
PE45203	262	60
PE45204	270	29
PE45205	298	72
PE45209	284	80
PE45210	280	12
PE45211	294	94
PE45215	274	13
PE45216	274	8
PE45217	273	66
PE45218	267	10
PE45222	267	12
PE45223	267	17
PE45224	266	82
PE45225	262	30
PE45227	291	90
PE45228	291	89
PE45229	291	96
PE45230	291	97
PE45231	291	95
PE45232	291	94
PE45233	291	91
PE45234	291	92
PE45235	291	93
PE45237	291	98
PE45239	248	79
PE45245	262	65
PE45248	282	2
PE45249	282	1
PE45250	259	19
PE45251	259	20
PE45252	259	21
PE45253	259	22
PE45254	259	25
PE45255	259	26
PE45256	259	27
PE45257	259	28
PE45261	259	29
PE45267	259	34

Model No.	Page	C/R
PE45274	256	46
PE45277	282	90
PE45282	271	53
PE45283	288	21
PE45284	266	93
PE45285	282	96
PE45287	282	95
PE45290	282	98
PE45292	272	23
PE45295	242	72
PE45296	242	73
PE45297	243	81
PE45298	242	80
PE45299	242	78
PE45300	242	79
PE45301	243	85
PE45302	243	91
PE45303	243	93
PE45304	243	5
PE45306	243	6
PE45307	254	88
PE45310	245	89
PE45311	245	90
PE45313	245	88
PE45314	245	87
PE45315	245	84
PE45316	245	86
PE45317	245	85
PE45318	245	83
PE45319	246	8
PE45320	246	7
PE45321	246	16
PE45322	246	17
PE45323	246	15
PE45324	246	10
PE45325	246	11
PE45326	246	18
PE45327	246	19
PE45328	246	9
PE45329	247	24
PE45330	247	25
PE45331	247	26
PE45332	247	23
PE45333	246	5
PE45334	246	21
PE45335	245	82
PE45336	245	81
PE45337	246	13
PE45338	246	12
PE45339	246	99
PE45340	246	20
PE45341	246	95
PE45342	246	96
PE45343	246	97
PE45344	246	98
PE45345	245	91
PE45346	245	92
PE45347	246	94
PE45348	245	93
PE45349	246	14
PE45350	246	1
PE45351	246	2
PE45352	246	3
PE45353	246	4
PE45354	247	22
PE45355	246	6
PE45356	262	26
PE45363	284	76
PE45366	284	75
PE45369	Web	
PE45370	285	89
PE45371	285	88
PE45372	Web	
PE45373	Web	
PE45374	Web	
PE45375	285	92
PE45376	285	87
PE45377	285	96
PE45378	285	2
PE45379	284	86
PE45380	285	94
PE45384	284	85
PE45385	284	84
PE45387	285	97
PE45388	285	99
PE45389	285	1
PE45390	285	93
PE45391	285	95
PE45395	248	91
PE45396	279	83
PE45397	275	71
PE45398	242	61
PE45400	241	29
PE45401	240	82
PE45402	238	29
PE45403	237	1
PE45404A	252	20
PE45404B	252	21
PE45404C	252	22
PE45404D	252	23
PE45404H	252	24
PE45404I	252	25
PE45404K	252	26
PE45404Z	252	27
PE45405	283	48
PE45406	283	49
PE45410	237	19
PE45411	239	66
PE45412	240	9
PE45413	237	23
PE45414	239	68
PE45415	240	16
PE45417	243	98
PE45418	243	87
PE45419	243	94
PE45420	242	69
PE45421	242	64
PE45422	242	66
PE45423	244	62
PE45424	244	29
PE45425	244	43
PE45426	263	96
PE45427	261	14
PE45428	262	55
PE45429	267	3
PE45430	266	89
PE45431	266	99

Model No.	Page	C/R
PE45432	271	93
PE45433	Web	
PE45434	271	64
PE45437	286	16
PE45440	269	54
PE45441	272	16
PE45442	270	32
PE45443	285	7
PE45444	287	78
PE45445	286	46
PE45446	260	68
PE45447	263	2
PE45448	262	29
PE45450	241	24
PE45451	241	25
PE45452	241	18
PE45453	241	17
PE45454	240	76
PE45455	240	75
PE45456	239	70
PE45457	239	69
PE45458	271	95
PE45459	271	94
PE45460	269	51
PE45461	269	52
PE45462	272	98
PE45463	272	97
PE45464	272	99
PE45465	272	1
PE45466	272	96
PE45467	241	30
PE45468	241	31
PE45469	241	32
PE45470	241	28
PE45471	241	33
PE45472	240	80
PE45473	240	79
PE45474	240	83
PE45475	240	84
PE45476	240	81
PE45477	238	30
PE45478	290	87
PE45479	267	26
PE45480	269	90
PE45481	269	89
PE45482	237	20
PE45483	240	12
PE45484	237	21
PE45485	240	13
PE45486	240	10
PE45487	240	11
PE45490	284	78
PE45491	284	77
PE45492	284	79
PE45493	285	90
PE45494	285	91
PE45496	284	81
PE45497	284	82
PE45498	284	83
PE45499	285	98
PE45502	263	97
PE45504	293	81
PE45505	261	18
PE45507	241	27
PE45508	241	26
PE45509	241	19
PE45510	241	20
PE45511	240	77
PE45512	240	78
PE45513	239	72
PE45514	239	71
PE45515	238	28
PE45516	238	31
PE45517	238	24
PE45518	238	25
PE45519	255	4
PE45520	293	69
PE45541	239	65
PE45543	270	7
PE45546	270	42
PE45547	272	50
PE45552	293	82
PE45554	272	37
PE45556	268	43
PE45560	273	99
PE45561	273	2
PE45562	273	5
PE45563	274	10
PE45564	274	12
PE45565	274	15
PE45566	273	98
PE45567	273	1
PE45568	273	6
PE45569	274	9
PE45570	274	11
PE45571	274	16
PE45572	273	62
PE45573	273	65
PE45574	273	68
PE45575	273	72
PE45576	273	76
PE45577	273	79
PE45578	273	61
PE45579	273	64
PE45580	273	69
PE45581	273	73
PE45582	273	75
PE45583	273	78
PE45584	273	63
PE45585	273	67
PE45586	273	71
PE45587	273	74
PE45588	273	77
PE45589	273	81
PE45590	241	50
PE45591	241	52
PE45592	241	54
PE45593	241	56
PE45594	241	51
PE45595	241	53
PE45596	241	55
PE45597	241	57
PE45598	241	37
PE45599	241	41
PE45600	241	44
PE45601	241	47
PE45602	241	35

Model No.	Page	C/R
PE45603	241	38
PE45604	241	42
PE45605	241	45
PE45606	241	36
PE45607	241	39
PE45608	241	43
PE45609	241	46
PE45610	240	99
PE45611	240	2
PE45612	240	4
PE45613	240	6
PE45614	240	98
PE45615	240	1
PE45616	240	3
PE45617	240	5
PE45618	240	88
PE45619	240	91
PE45620	240	94
PE45621	240	97
PE45622	240	87
PE45623	240	89
PE45624	240	92
PE45625	240	95
PE45626	240	86
PE45627	240	90
PE45628	240	93
PE45629	240	96
PE45630	238	36
PE45631	238	35
PE45632	238	33
PE45633	238	34
PE45639	287	73
PE45640	244	41
PE45650	242	63
PE45651	242	65
PE45652	242	68
PE45653	242	71
PE45654	243	82
PE45655	243	92
PE45656	243	97
PE45657	243	2
PE45658	243	83
PE45659	243	84
PE45660	244	28
PE45661	244	42
PE45662	244	61
PE45663	245	71
PE45664	261	7
PE45665	262	48
PE45666	263	90
PE45667	264	28
PE45668	266	74
PE45669	266	76
PE45670	266	78
PE45671	266	79
PE45672	266	73
PE45673	239	58
PE45674	239	61
PE45675	239	62
PE45676	239	64
PE45677	239	59
PE45678	269	96
PE45679	271	54
PE45680	271	83
PE45681	272	34
PE45682	266	87
PE45683	266	96
PE45684	267	2
PE45685	267	8
PE45686	243	4
PE4CQ1013	251	4
PE45259TR1	259	23
PE45259TR750	259	24
PE45262TR1	259	30
PE45262TR750	259	31
PE45265TR1	259	33
PE45265TR500	259	32
PE45278TR1	280	30
PE45278TR1500	280	29
PE5001	357	6
PE5004-KIT	357	8
PE5006	357	5
PE5007	357	7
PE5008	357	9
PE5009	357	10
PE5010	357	12
PE5011	356	4
PE5012	357	11
PE5014	355	2
PE5019	356	3
PE5200	355	1
PE5500-KIT	348	6
PE5501-KIT	348	14
PE51021	266	80
PE51023	60	18
PE51024	60	7
PE51025	60	6
PE51026	66	89
PE51027	63	8
PE51028	62	81
PE51034	62	87
PE51037	63	89
PE51040	63	90
PE51050	60	25
PE51055	66	88
PE51056	66	87
PE51058	62	79
PE51059	62	78
PE51061	62	85
PE51062	62	82
PE51063	62	83
PE51064	62	86
PE51065	62	88
PE51066	63	95
PE51067	63	92
PE51068	63	94
PE51077	66	97
PE51078	66	98
PE51080	66	2
PE51081	66	5
PE51082	66	3
PE51083	66	4
PE51084	66	11
PE51085	66	12
PE51087	66	1
PE51088	66	99
PE51089	65	83

Model No.	Page	C/R
PE51090	66	95
PE51096	62	80
PE51113	63	1
PE51117A	66	91
PE51119	66	90
PE51121	66	93
PE51123	66	94
PE51125A	66	15
PE51127	66	16
PE51129	60	26
PE51133	66	96
PE51134	66	14
PE51135A	66	13
PE51136	63	12
PE51142	66	6
PE51143	66	7
PE51144	66	8
PE51146	65	64
PE51152	65	77
PE51154	65	76
PE51157	65	75
PE51158	62	77
PE51159	65	65
PE51160	65	66
PE51161	65	67
PE51164	65	81
PE51165	65	82
PE51166	65	80
PE51167	266	81
PE51171	61	39
PE51172	62	84
PE51173	66	92
PE51194	65	47
PE51195	65	43
PE51196	65	46
PE51197	65	45
PE51198	65	44
PE51199	64	42
PE51200	64	41
PE51201	65	58
PE51202	65	59
PE51203	65	57
PE51204	65	51
PE51205	65	54
PE51206	65	50
PE51207	65	55
PE51208	65	52
PE51209	65	53
PE51210	65	56
PE51211	65	62
PE51212	63	91
PE51213	65	49
PE51214	65	60
PE51215	65	61
PE51216	65	48
PE51217	62	65
PE51218	62	67
PE51219	62	69
PE51220	62	71
PE51221	62	73
PE51222	62	75
PE51223	62	66
PE51224	62	68
PE51225	62	70
PE51226	62	72
PE51227	62	74
PE51228	62	76
PE51239	60	3
PE51AK1000	67	54
PE51AK1001	67	55
PE51AK1002	67	56
PE51AK1003	67	57
PE51AK1004	67	61
PE51FP1001	60	22
PE51FP1002	60	21
PE51FP1003	60	19
PE51FP1004	60	20
PE51FP1005	60	13
PE51FP1005	60	14
PE51FP1006	60	5
PE51FP1007	60	8
PE51FP1008	60	9
PE51FP1008	60	10
PE51FP1009	61	59
PE51FP1010	60	23
PE51FP1011	60	24
PE51FP1012	60	1
PE51FP1013	60	2
PE51FP1014	60	4
PE51FP1015	64	39
PE51FP1016	64	40
PE51GM1001	67	53
PE51GM1002	63	99
PE51GPS1000	67	62
PE51GPS1001	67	63
PE51GPS1002	67	59
PE51GPS1003	67	60
PE51GPS1004	63	98
PE51GPS1005	67	58
PE51LP1001	61	53
PE51LP1002	61	54
PE51MO1001	63	5
PE51MO1002	63	6
PE51MO1003	63	9
PE51MO1004	63	11
PE51MP1000	67	41
PE51MP1001	67	42
PE51MP1002	67	43
PE51MP1003	67	45
PE51MP1004	67	44
PE51MP1005	67	47
PE51MP1006	67	48
PE51MP1007	67	49
PE51MP1008	67	50
PE51MP1009	67	46
PE51MP1010	67	52
PE51MP1011	67	51
PE51OM1001	64	35
PE51OM1002	64	33
PE51OM1003	64	34
PE51OM1004	64	30
PE51OM1005	64	31
PE51OM1006	64	36
PE51OM1007	64	28
PE51OM1008	64	26
PE51OM1009	64	25
PE51OM1010	64	27

Model No.	Page	C/R
PE51OM1011	64	29
PE51OM1012	64	32
PE51OM1013	64	16
PE51OM1014	64	15
PE51OM1015	64	17
PE51OM1016	64	18
PE51OM1017	64	20
PE51OM1018	64	21
PE51OM1019	64	19
PE51OM1020	64	13
PE51OM1021	64	14
PE51OM1022	63	7
PE51OM1023	63	10
PE51OM1024	64	22
PE51OM1025	64	23
PE51OM1026	64	24
PE51OM1027	65	69
PE51OM1028	65	73
PE51OM1029	65	70
PE51OM1030	65	68
PE51OM1031	64	37
PE51OM1032	64	38
PE51PD1001	61	52
PE51PD1002	61	51
PE51PD1003	61	50
PE51PD1004	61	47
PE51PD1005	61	48
PE51PD1006	61	49
PE51RD1001	66	34
PE51RD1002	66	35
PE51RD1003	66	36
PE51RD1004	66	37
PE51RD1005	66	39
PE51RD1006	66	38
PE51RD1007	66	32
PE51RD1008	66	17
PE51RD1009	66	18
PE51RD1010	66	20
PE51RD1011	66	21
PE51RD1012	66	22
PE51RD1013	66	26
PE51RD1014	66	29
PE51RD1015	66	30
PE51RD1016	66	31
PE51RD1017	66	33
PE51RD1018	66	23
PE51RD1019	66	19
PE51RD1020	66	24
PE51RD1021	66	40
PE51RD1022	66	25
PE51RD1023	66	27
PE51RD1024	66	28
PE51RD1025	66	9
PE51RD1026	66	10
PE51RD1027	65	78
PE51RD1028	65	79
PE51RD1030	65	72
PE51RD1031	65	71
PE51RD1032	65	74
PE51SE1001	61	61
PE51SE1002	62	62
PE51SE1003	61	58
PE51SE1004	61	57
PE51SE1005	61	56
PE51SE1006	61	55
PE51SE1007	62	64
PE51SE1008	62	63
PE51SE1009	61	60
PE51TM1000	63	93
PE51TM1001	63	97
PE51TW1000	65	63
PE51YA1001	61	42
PE51YA1002	61	43
PE51YA1003	61	44

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE6031	301	54
PE6032	344	93
PE6033	347	15
PE6034	345	27
PE6035	345	30
PE6036	345	32
PE6037	345	47
PE6038	345	50
PE6039	345	71
PE6040	346	76
PE6041	346	90
PE6043	346	96
PE6046	300	16
PE6057	300	10
PE6058	300	11
PE6059	300	21
PE6069	343	48
PE6070	343	11
PE6071	343	50
PE6072	343	49
PE6073	343	53
PE6075	344	89
PE6076	344	92
PE6077	343	52
PE6078	343	51
PE6079	343	55
PE6080	343	54
PE6081	344	97
PE6082	344	96
PE6083	344	4
PE6084	344	3
PE6085	343	4
PE6086	343	3
PE6087	343	6
PE6088	343	5
PE6089	344	9
PE6090	344	8
PE6091	344	13
PE6092	344	12
PE6095	345	21
PE6096	345	22
PE6097	345	19
PE6098	345	20
PE6099	345	23
PE6100	344	15
PE6101	345	28
PE6102	345	31
PE6103	345	33
PE6104	345	34
PE6105	345	25
PE6106	345	45
PE6107	345	40
PE6108	300	15
PE6109	300	17
PE6110	300	18
PE6111	300	19
PE6113	300	22
PE6114	300	23
PE6115	300	24
PE6116	300	28
PE6117	301	29
PE6118	301	30
PE6119	301	33
PE6120	301	34
PE6121	301	35
PE6122	301	37
PE6124	301	39
PE6125	301	36
PE6126	301	38
PE6127	301	47
PE6128	301	49
PE6129	301	51
PE6130	301	53
PE6131	301	55
PE6132	301	57
PE6133	301	61
PE6134	301	60
PE6135	301	63
PE6136	301	62
PE6137	346	87
PE6138	345	24
PE6139	345	16
PE6140	345	35
PE6141	345	26
PE6144	301	42
PE6146	343	7
PE6150	343	45
PE6154	344	84
PE6156	344	82
PE6160	344	62
PE6161	344	60
PE6162	343	9
PE6163	343	8
PE6165	346	10
PE6168	346	92
PE6169	345	60
PE6172	344	6
PE6173	343	26
PE6174	343	24
PE6175	343	28
PE6176	344	72
PE6177	344	71
PE6178	343	21
PE6179	343	19
PE6180	344	70
PE6181	343	13
PE6182	343	2
PE6183	343	12
PE6184	343	1
PE6185	345	29
PE6186	345	18
PE6187	345	17
PE6188	345	64
PE6189	345	63
PE6190	344	77
PE6191	345	59
PE6193	301	46
PE6194	301	44
PE6195	301	45
PE6196	344	79
PE6197	346	86
PE6198	345	67
PE6199	343	41
PE6201A	386	15
PE6202	346	9
PE6202-25PK	346	8
PE6202-100PK	346	7

Model No.	Page	C/R
PE6203	345	48
PE6204	345	49
PE6205	345	44
PE6206	345	46
PE6207	345	51
PE6208	345	52
PE6209	345	41
PE6210	345	42
PE6211	345	72
PE6212	346	75
PE6213	345	66
PE6214	345	70
PE6215	346	77
PE6216	346	78
PE6217	345	61
PE6218	345	62
PE6219	346	95
PE6220	346	98
PE6222	346	94
PE6224	346	93
PE6227	344	68
PE6228	345	43
PE6229	344	10
PE6230	346	2
PE6231	346	3
PE6232	345	73
PE6233	345	68
PE6234	345	69
PE6235	343	15
PE6236	343	14
PE6238	345	58
PE6239	346	89
PE6240	300	20
PE6241	343	46
PE6242	344	69
PE6243	344	67
PE6248	344	85
PE6249	344	86
PE6251	301	58
PE6800	385	88
PE6801	385	96
PE6802	385	3
PE6803	385	10
PE6804	386	16
PE6805	386	18
PE6806	386	23
PE6808	386	32
PE6809	385	89
PE6810	385	97
PE6811	385	4
PE6812	385	11
PE6814	386	19
PE6815	386	24
PE6818	385	93
PE6819	385	1
PE6820	385	8
PE6823	386	21
PE6824	386	29
PE6828	385	2
PE6829	385	9
PE6832	386	22
PE6833	386	30
PE6834	386	31
PE6835	386	35
PE6836	386	17
PE6TR000	347	14
PE6TR001	347	17
PE6TR002	343	57
PE6TR003	346	13
PE6TR004	346	11
PE6TR005	343	58
PE6TR007	344	80
PE6TR008	344	81
PE6TR009	344	87
PE6TR010	344	83
PE6TR011	344	91
PE6TR012	344	88
PE6TR014	344	5
PE6TR015	344	11
PE6TR016	344	7
PE6TR028	344	14
PE6TR029	345	65
PE6TR040	346	12
PE6TR1000	345	53
PE6TR1001	346	74
PE6TR1002	346	97
PE6TR1003	346	1
PE6TR1004	346	4
PE6TR1005	346	5
PE6TR1006	346	6
PE6TR1013	344	78
PE6TR1014	343	47
PE6TR1020	345	39
PE6TR1021	345	38
PE6TR1022	345	36
PE6TR1023	345	37
PE6TR1024	345	57
PE6TR1025	345	56
PE6TR1026	345	54
PE6TR1027	345	55
PE6TR1028	346	82
PE6TR1029	346	81
PE6TR1030	346	79
PE6TR1031A	346	80
PE6TR1032A	346	91
PE6TR1032F	346	93
PE6TR1033A	346	85
PE6TR1033F	346	88
PE6TR1035A	346	83
PE6TR1035F	346	84
PE6TR1036	344	95
PE6TR1037	343	56
PE6TR1038	343	44
PE6TR1039	344	59
PE6TR1040	344	61
PE6TR1041	343	34
PE6TR1042	343	35
PE6TR1044	343	36
PE6TR1045	344	73
PE6TR1046	344	74
PE6TR1047	344	75
PE6TR1048	344	76
PE6TR1050	343	42
PE6TR1051	343	43
PE6TR1052	344	94
PE6TR1100	343	17
PE6TR1101	343	16

Model No.	Page	C/R
PE6TR1102	343	18
PE6TR1103	343	22
PE6TR1104	343	20
PE6TR1105	343	23
PE6TR1106	343	27
PE6TR1107	343	25
PE6TR1108	343	29
PE6TR1109	343	30
PE6TR1110	343	31
PE6TR1111	343	32
PE6TR1112	343	33
PE6TR1113	344	63
PE6TR1114	344	64
PE6TR1115	344	65
PE6TR1116	344	66
PE6TR1117	343	37
PE6TR1118	343	38
PE6TR1119	343	39
PE6TR1120	343	40
PE6TR671	344	1
PE6TR673	344	2
PE6TR675	344	98
PE6TR677	344	99
PE7000	70	7
PE7001	72	26
PE7002	71	8
PE7003	71	12
PE7004	72	18
PE7005	73	30
PE7006	347	18
PE7007	347	19
PE7008	83	52
PE7009	82	44
PE7010	75	46
PE7013	75	41
PE7014	74	39
PE7015	75	49
PE7016	75	51
PE7017	76	61
PE7018	77	78
PE7019	78	97
PE7020	79	4
PE7021	80	17
PE7022	81	27
PE7024	71	13
PE7024.1	71	14
PE7025	75	45
PE7026	80	15
PE7027	347	26
PE7028	347	31
PE7029	82	45
PE7030	74	35
PE7031	82	39
PE7032	82	40
PE7034	84	55
PE7035	84	60
PE7039	74	36
PE7040	75	44
PE7041	76	55
PE7042	77	84
PE7044	82	49
PE7045	73	29
PE7046	70	2
PE7047	72	19
PE7048	75	48
PE7049	72	17
PE7050	82	46
PE7051	74	34
PE7052	75	42
PE7053	76	52
PE7054	77	81
PE7055	79	7
PE7056	81	32
PE7057	82	47
PE7061	84	62
PE7062	84	61
PE7063	84	63
PE7064	84	64
PE7066	347	21
PE7067	347	20
PE7068	347	22
PE7070	347	27
PE7071	347	25
PE7072	347	23
PE7073	347	28
PE7074	347	30
PE7075	347	34
PE7076	347	36
PE7077	347	38
PE7078	347	40
PE7079	347	41
PE7081	347	42
PE7082	347	43
PE7083	347	32
PE7085-2	82	41
PE7085-20	82	41
PE7087-0	73	32
PE7087-1	73	32
PE7087-2	73	32
PE7087-3	73	32
PE7087-4	73	32
PE7087-5	73	32
PE7087-6	73	32
PE7087-7	74	32
PE7087-8	74	32
PE7087-9	74	32
PE7087-10	74	32
PE7087-12	74	32
PE7087-15	74	32
PE7087-20	74	32
PE7087-30	74	32
PE7088-0	70	6
PE7088-1	70	6
PE7088-2	70	6
PE7088-3	70	6
PE7088-4	70	6
PE7088-5	70	6
PE7088-6	70	6
PE7088-7	70	6
PE7088-8	70	6
PE7088-9	70	6
PE7088-10	70	6
PE7088-12	70	6
PE7088-15	70	6
PE7088-20	70	6
PE7088-30	70	6
PE7089-10	70	5

Model No.	Page	C/R
PE7089-12	70	5
PE7089-15	70	5
PE7089-20	70	5
PE7089-30	70	5
PE7089-0	70	5
PE7089-1	70	5
PE7089-2	70	5
PE7089-3	70	5
PE7089-4	70	5
PE7089-5	70	5
PE7089-6	70	5
PE7089-7	70	5
PE7089-8	70	5
PE7089-9	70	5
PE7090-3	71	15
PE7090-10	71	15
PE7090-15	71	15
PE7090-20	71	15
PE7090-30	71	15
PE7091-0	72	27
PE7091-1	72	27
PE7091-2	72	27
PE7091-3	72	27
PE7091-4	72	27
PE7091-5	72	27
PE7091-6	72	27
PE7091-7	72	27
PE7091-10	72	27
PE7091-12	72	27
PE7091-15	72	27
PE7091-20	73	27
PE7091-30	73	27
PE7091-40	73	27
PE7092-1	73	31
PE7092-2	73	31
PE7092-3	73	31
PE7092-4	73	31
PE7092-5	73	31
PE7092-6	73	31
PE7092-7	73	31
PE7092-8	73	31
PE7092-9	73	31
PE7092-10	73	31
PE7092-12	73	31
PE7092-15	73	31
PE7092-20	73	31
PE7092-30	73	31
PE7092-40	73	31
PE7100	330	52
PE7102	330	53
PE7103	330	54
PE7139	331	63
PE7139-CART	323	27
PE7140	331	64
PE7161-1	71	11
PE7161-2	71	11
PE7161-3	71	11
PE7161-4	71	11
PE7161-5	71	11
PE7161-6	71	11
PE7161-8	71	11
PE7161-9	71	11
PE7161-10	71	11
PE7161-12	71	11
PE7161-20	71	11
PE7161-30	71	11
PE7161-40	71	11
PE7162-1	73	28
PE7162-2	73	28
PE7162-3	73	28
PE7162-4	73	28
PE7162-5	73	28
PE7162-6	73	28
PE7162-7	73	28
PE7162-8	73	28
PE7162-9	73	28
PE7162-10	73	28
PE7162-12	73	28
PE7162-15	73	28
PE7162-20	73	28
PE7162-30	73	28
PE7162-40	73	28
PE7176	330	55
PE7201-3	79	11
PE7201-6	79	11
PE7201-10	79	11
PE7201-20	79	11
PE7201-30	79	11
PE7201-40	79	11
PE7201-50	79	11
PE7201-60	79	11
PE7202-3	80	23
PE7202-6	80	23
PE7202-10	80	23
PE7202-20	80	23
PE7202-30	80	23
PE7202-40	80	23
PE7202-50	80	23
PE7202-60	81	23
PE7203-3	79	9
PE7203-6	79	9
PE7203-10	79	9
PE7203-20	79	9
PE7203-30	79	9
PE7203-40	79	9
PE7203-50	79	9
PE7203-60	79	9
PE7204-3	79	12
PE7204-6	79	12
PE7204-10	79	12
PE7204-20	79	12
PE7204-30	79	12
PE7204-40	79	12
PE7204-50	79	12
PE7204-60	79	12
PE7205-3	80	16
PE7205-6	80	16
PE7205-10	80	16
PE7205-20	80	16
PE7205-30	80	16
PE7205-40	80	16
PE7205-50	80	16
PE7205-60	80	16
PE7206-3	81	24
PE7206-6	81	24
PE7206-10	81	24
PE7206-20	81	24

Model No.	Page	C/R
PE7206-30	81	24
PE7206-40	81	24
PE7206-50	81	24
PE7206-60	81	24
PE7207-3	80	13
PE7207-6	80	13
PE7207-10	80	13
PE7207-20	80	13
PE7207-30	80	13
PE7207-40	80	13
PE7207-50	80	13
PE7207-60	80	13
PE7208-3	81	25
PE7208-6	81	25
PE7208-10	81	25
PE7208-20	81	25
PE7208-30	81	25
PE7208-40	81	25
PE7208-50	81	25
PE7208-60	81	25
PE7210-30	81	33
PE7211-3	79	10
PE7211-6	79	10
PE7211-10	79	10
PE7211-20	79	10
PE7211-30	79	10
PE7211-40	79	10
PE7211-50	79	10
PE7211-60	79	10
PE7212-3	80	14
PE7212-6	80	14
PE7212-10	80	14
PE7212-20	80	14
PE7212-30	80	14
PE7212-40	80	14
PE7212-50	80	14
PE7212-60	80	14
PE7213-3	80	20
PE7213-6	80	20
PE7213-10	80	20
PE7213-20	80	20
PE7213-30	80	20
PE7213-40	80	20
PE7213-50	80	20
PE7213-60	80	20
PE7214-3	81	26
PE7214-6	81	26
PE7214-10	81	26
PE7214-20	81	26
PE7214-30	81	26
PE7214-40	81	26
PE7214-50	81	26
PE7214-60	81	26
PE7218-3	81	34
PE7221-3	81	30
PE7221-6	81	30
PE7221-10	81	30
PE7221-20	81	30
PE7221-40	81	30
PE7221-50	81	30
PE7221-60	81	30
PE7227-3	81	28
PE7227-6	81	28
PE7227-10	81	28
PE7227-20	81	28
PE7227-30	81	28
PE7227-40	81	28
PE7227-50	81	28
PE7227-60	81	28
PE7228-3	81	31
PE7228-20	81	31
PE7228-30	81	31
PE7228-50	81	31
PE7237-30	80	22
PE7301-1	323	84
PE7301-2	323	85
PE7301-3	323	82
PE7301-4	322	81
PE7301-200CART	323	25
PE7301-2000CART	323	26
PE7310-50	77	86
PE7310-3	77	86
PE7310-6	77	86
PE7310-10	77	86
PE7310-20	77	86
PE7310-30	77	86
PE7310-40	77	86
PE7311-50	78	99
PE7311-3	78	99
PE7311-6	78	99
PE7311-10	78	99
PE7311-20	78	99
PE7311-30	78	99
PE7311-40	78	99
PE7312-50	77	83
PE7312-3	77	85
PE7312-6	77	85
PE7312-10	77	85
PE7312-20	77	85
PE7312-30	77	85
PE7312-40	77	85
PE7313-50	77	87
PE7313-3	77	87
PE7313-6	77	87
PE7313-10	77	87
PE7313-20	78	87
PE7313-30	78	87
PE7313-40	78	87
PE7314-50	78	92
PE7314-3	78	92
PE7314-6	78	92
PE7314-10	78	92
PE7314-20	78	92
PE7314-30	78	92
PE7314-40	78	92
PE7315-50	78	1
PE7315-3	78	1
PE7315-6	78	1
PE7315-10	78	1
PE7315-20	78	1
PE7315-30	78	1
PE7315-40	78	1
PE7316-50	78	88
PE7316-3	78	90
PE7316-6	78	90
PE7316-10	78	90
PE7316-20	78	90

Model No.	Page	C/R
PE7316-30	78	90
PE7316-40	78	90
PE7317-50	79	2
PE7317-3	79	2
PE7317-6	79	2
PE7317-10	79	2
PE7317-20	79	2
PE7317-30	79	2
PE7317-40	79	2
PE7321-50	78	89
PE7321-3	78	91
PE7321-6	78	91
PE7321-10	78	91
PE7321-20	78	91
PE7321-30	78	91
PE7321-40	78	91
PE7322-50	78	96
PE7322-3	78	98
PE7322-6	78	98
PE7322-10	78	98
PE7322-20	78	98
PE7322-30	78	98
PE7322-40	78	98
PE7323-50	79	3
PE7323-3	79	3
PE7323-6	79	3
PE7323-10	79	3
PE7323-20	79	3
PE7323-30	79	3
PE7323-40	79	3
PE7337-6	79	6
PE7337-10	79	6
PE7337-20	79	6
PE7337-30	79	6
PE7337-40	79	6
PE7337-50	79	6
PE7351-10	79	8
PE7351-20	79	8
PE7351-40	79	8
PE7351-50	79	8
PE7357-50	77	77
PE7357-10	77	79
PE7357-20	77	79
PE7357-30	77	79
PE7357-40	77	79
PE7357-3	77	79
PE7357-6	77	79
PE7363-10	77	80
PE7363-20	77	80
PE7363-30	77	80
PE7363-6	77	80
PE7363-40	77	80
PE7366-50	76	58
PE7366-10	76	58
PE7366-20	76	58
PE7366-30	76	58
PE7366-40	76	58
PE7366-3	76	58
PE7366-6	76	58
PE7367-50	76	60
PE7367-10	76	63
PE7367-20	76	65
PE7367-30	76	67
PE7367-40	76	69
PE7367-3	76	71
PE7367-6	76	71
PE7369-50	77	73
PE7369-10	77	73
PE7369-20	77	73
PE7369-30	77	73
PE7369-40	77	73
PE7369-3	77	73
PE7369-6	77	73
PE7370-50	76	72
PE7370-3	76	72
PE7370-6	76	72
PE7370-10	76	72
PE7370-20	76	72
PE7370-30	77	72
PE7370-40	77	72
PE7371-50	77	74
PE7371-10	77	74
PE7371-3	77	74
PE7371-6	77	74
PE7371-20	77	74
PE7371-30	77	74
PE7371-40	77	74
PE7372-30	77	75
PE7375-20	77	82
PE7375-30	77	82
PE7375-40	77	82
PE7379-50	76	54
PE7379-10	76	56
PE7379-20	76	56
PE7379-30	76	56
PE7379-40	76	56
PE7379-3	76	56
PE7379-6	76	56
PE7380-50	76	57
PE7380-3	76	57
PE7380-6	76	57
PE7380-10	76	57
PE7380-20	76	57
PE7380-30	76	57
PE7380-40	76	57
PE7385-3	80	18
PE7385-6	80	18
PE7385-10	80	18
PE7385-20	80	18
PE7385-30	80	18
PE7385-40	80	18
PE7386-3	75	47
PE7386-6	75	47
PE7386-10	75	47
PE7386-15	75	47
PE7386-20	75	47
PE7386-30	75	47
PE7386-40	75	47
PE7387-10	81	36
PE7387-20	81	36
PE7387-30	81	36
PE7387-40	81	36
PE7388-3	78	93
PE7388-6	78	93
PE7388-10	78	93
PE7388-15	78	93
PE7388-20	78	93

Model No.	Page	C/R
PE7388-30	78	93
PE7388-40	78	93
PE7389-3	78	94
PE7389-6	78	94
PE7389-10	78	94
PE7389-15	78	94
PE7389-20	78	94
PE7389-30	78	94
PE7389-40	78	94
PE7390-1	74	37
PE7390-2	74	37
PE7390-3	74	37
PE7390-6	74	37
PE7390-10	74	37
PE7390-15	74	37
PE7390-20	74	37
PE7390-30	74	37
PE7391-1	74	40
PE7391-2	74	40
PE7391-3	74	40
PE7391-6	74	40
PE7391-10	74	40
PE7391-15	74	40
PE7391-20	74	40
PE7391-30	74	40
PE7392-1	76	59
PE7392-2	76	59
PE7392-3	76	59
PE7392-6	76	59
PE7392-10	76	59
PE7392-20	76	59
PE7392-30	76	59
PE7392-40	76	59
PE7393-3	77	76
PE7393-10	77	76
PE7393-20	77	76
PE7393-30	77	76
PE7393-40	77	76
PE7394-2	78	95
PE7394-3	78	95
PE7394-6	78	95
PE7394-10	78	95
PE7394-30	78	95
PE7394-40	78	95
PE7395-0	71	16
PE7395-1	71	16
PE7395-2	71	16
PE7395-3	71	16
PE7395-4	71	16
PE7395-5	71	16
PE7395-6	71	16
PE7395-7	71	16
PE7395-8	71	16
PE7395-9	71	16
PE7395-10	71	16
PE7395-12	71	16
PE7395-15	72	16
PE7395-20	72	16
PE7396-1	82	48
PE7396-2	82	48
PE7396-3	82	48
PE7396-4	82	48
PE7396-5	82	48
PE7396-6	82	48
PE7396-7	82	48
PE7396-8	82	48
PE7396-9	82	48
PE7396-10	82	48
PE7396-16	82	48
PE7396-20	82	48
PE7403-1	70	4
PE7403-2	70	4
PE7403-3	70	4
PE7403-4	70	4
PE7403-5	70	4
PE7403-6	70	4
PE7403-7	70	4
PE7403-8	70	4
PE7403-9	70	4
PE7403-10	70	4
PE7403-20	70	4
PE7403-30	70	4
PE7421-3	80	19
PE7421-6	80	19
PE7421-10	80	19
PE7421-20	80	19
PE7421-30	80	19
PE7421-40	80	19
PE7422	85	65
PE7423-30	82	43
PE7423-40	82	43
PE7424-03	80	21
PE7424-06	80	21
PE7424-10	80	21
PE7424-20	80	21
PE7424-30	80	21
PE7424-40	80	21
PE7425-10	81	29
PE7425-20	81	29
PE7425-30	81	29
PE7425-40	81	29
PE7426-03	76	62
PE7426-06	76	62
PE7426-10	76	64
PE7426-20	76	66
PE7426-30	76	68
PE7426-40	76	70
PE7427-03	79	5
PE7427-06	79	5
PE7427-10	79	5
PE7427-15	79	5
PE7427-20	79	5
PE7427-30	79	5
PE7427-40	79	5
PE7428-01	75	50
PE7428-02	75	50
PE7428-03	75	50
PE7428-06	75	50
PE7428-10	75	50
PE7428-15	75	50
PE7428-20	75	50
PE7428-30	75	50
PE70A1000	85	94
PE70A1001	83	53
PE70A1008	83	54
PE70A1009	72	20
PE70A1010	72	21

Model No.	Page	C/R
PE70A1011	72	22
PE70A1012	72	23
PE70A1014	72	24
PE70A1015	72	25
PE70A1017	85	92
PE70A1021	83	51
PE70A1022	84	57
PE70A1023	84	59
PE70A1024	84	56
PE70A1025	84	58
PE70A1031	85	93
PE70A2000	85	96

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE71S5002	335	98
PE71S5003	335	1
PE71S5004	335	2
PE71S5005	335	96
PE71S5006	335	99
PE71S6052	330	36
PE71S6053	330	37
PE71S6054	330	38
PE71S6055	330	39
PE71S6056	330	50
PE71S6057	330	51
PE71S6058	324	19
PE71S6059	324	20
PE71S6060	326	9
PE71S6063	327	14
PE71S6064	328	63
PE71S6065	328	78
PE71S6066	328	79
PE71S6067	328	81
PE71S6068	328	82
PE71S6069	328	80
PE71S6070	328	77
PE71S6071	328	83
PE71S6072	326	99
PE71S6073	326	1
PE71S6074	329	6
PE71S6075	329	11
PE71S6076	327	27
PE71S6077	329	7
PE71S6078	328	71
PE71S6079	327	56
PE71S6080	327	25
PE71S6082	326	2
PE71S6083	327	28
PE71S6084	328	70
PE71S6085	329	35
PE71S6087	330	48
PE71S6088	330	49
PE71S6092	330	56
PE71S6098	325	63
PE71S6103	325	65
PE71S6106	325	67
PE71S6109	325	66
PE71S6110	325	64
PE71S6122	326	79
PE71S6123	326	80
PE71S6130	325	59
PE71S6131	325	60
PE71S6137	326	73
PE71S6140	325	68
PE71S6143	326	78
PE71S6150	324	21
PE71S6155	325	27
PE71S6156	325	24
PE71S6157	325	25
PE71S6158	324	22
PE71S6159	325	23
PE71S6160	324	17
PE71S6161	324	18
PE71S6162	325	28
PE71S6163	325	29
PE71S6164	325	26
PE71S6166	325	35
PE71S6167	325	36
PE71S6168	325	30
PE71S6169	325	31
PE71S6170	325	43
PE71S6171	325	44
PE71S6172	325	40
PE71S6175	325	37
PE71S6177	325	32
PE71S6178	325	45
PE71S6179	325	46
PE71S6180	325	41
PE71S6181	325	42
PE71S6183	324	9
PE71S6184	324	6
PE71S6185	324	7
PE71S6186	324	14
PE71S6187	324	15
PE71S6189	324	11
PE71S6191	324	10
PE71S6192	324	8
PE71S6194	324	16
PE71S6196	324	12
PE71S6197	324	13
PE71S6199	324	5
PE71S6200	324	3
PE71S6201	324	4
PE71S6202	325	38
PE71S6203	325	39
PE71S6204	325	33
PE71S6205	325	34
PE71S6206	324	1
PE71S6207	324	2
PE71S6208	332	6
PE71S6209	331	70
PE71S6210	332	2
PE71S6211	333	39
PE71S6212	333	59
PE71S6213	334	83
PE71S6214	331	71
PE71S6215	332	3
PE71S6216	333	40
PE71S6217	333	60
PE71S6218	334	84
PE71S6219	332	32
PE71S6220	331	84
PE71S6221	332	29
PE71S6222	333	48
PE71S6223	333	70
PE71S6224	334	85
PE71S6225	331	85
PE71S6226	332	30
PE71S6227	333	49
PE71S6228	333	71
PE71S6229	334	86
PE71S6230	331	66
PE71S6231	331	72
PE71S6232	331	74
PE71S6233	331	77
PE71S6234	331	78
PE71S6235	331	79
PE71S6236	331	73
PE71S6237	332	96
PE71S6238	332	9
PE71S6239	332	10
PE71S6240	332	11
PE71S6241	332	5
PE71S6242	333	38
PE71S6243	333	41
PE71S6244	333	43
PE71S6245	333	44
PE71S6246	333	45
PE71S6247	333	46
PE71S6248	333	42
PE71S6249	333	58
PE71S6250	333	61
PE71S6251	333	63
PE71S6252	333	64
PE71S6253	333	65
PE71S6254	333	66
PE71S6255	333	62
PE71S6258	331	80
PE71S6259	331	86
PE71S6260	331	88
PE71S6261	331	91
PE71S6262	331	92
PE71S6263	331	93
PE71S6264	331	87
PE71S6265	332	18
PE71S6266	332	35
PE71S6267	332	36
PE71S6268	332	37
PE71S6269	332	31
PE71S6270	333	47
PE71S6271	333	50
PE71S6272	333	52
PE71S6273	333	53
PE71S6274	333	54
PE71S6275	333	55
PE71S6276	333	51
PE71S6277	333	69
PE71S6278	333	72
PE71S6279	333	74
PE71S6280	333	76
PE71S6281	333	78
PE71S6282	333	79
PE71S6283	333	73
PE71S6284	333	77
PE71S6285	333	77
PE71S6286	334	88
PE71S6287	334	89
PE71S6288	334	91
PE71S6289	334	92
PE71S6290	334	93
PE71S6291	334	94
PE71S6292	334	90
PE71S6293	325	48
PE71S6298	325	50
PE71S6300	325	49
PE71S6301	325	54
PE71S6302	325	52
PE71S6304	325	53
PE71S6306	325	51
PE71S6309	325	61
PE71S6310	325	62
PE71S6313	325	57
PE71S6314	325	58
PE71S6315	325	55
PE71S6316	325	56
PE71S6317	326	72
PE71S6318	325	71
PE71S6319	325	75
PE71S6320	325	70
PE71S6321	326	74
PE71S6322	326	75
PE71S6323	326	76
PE71S6324	326	77
PE71S6326	325	47
PE71S6329	328	75
PE71S6330	328	76
PE71S6331	330	46
PE71S6332	329	33
PE71S6333	330	44
PE71S6334	329	31
PE71S6335	330	40
PE71S6336	330	42
PE71S6337	330	41
PE71S6338	330	43
PE71S6339	330	47
PE71S6340	329	34
PE71S6341	330	45
PE71S6342	329	32
PE71S6347	326	6
PE71S6348	326	87
PE71S6349	328	85
PE71S6350	327	13
PE71S6351	326	5
PE71S6352	329	96
PE71S6353	328	91
PE71S6354	326	10
PE71S6355	326	11
PE71S6356	327	40
PE71S6357	327	41
PE71S6358	329	99
PE71S6359	329	1
PE71S6360	329	19
PE71S6361	329	20
PE71S6362	329	2
PE71S6363	327	15
PE71S6364	329	4
PE71S6365	329	5
PE71S6366	329	25
PE71S6367	329	26
PE71S6368	327	17
PE71S6369	327	18
PE71S6370	327	50
PE71S6371	327	51
PE71S6372	329	8
PE71S6373	327	19
PE71S6374	327	23
PE71S6375	327	24
PE71S6376	329	9
PE71S6377	329	10
PE71S6378	329	28
PE71S6379	329	29
PE71S6380	327	21
PE71S6381	327	22
PE71S6382	327	59
PE71S6383	327	60
PE71S6384	327	26
PE71S6385	326	96
PE71S6386	326	98
PE71S6387	328	88
PE71S6388	327	30
PE71S6389	327	31
PE71S6390	328	89
PE71S6391	326	7
PE71S6392	326	8
PE71S6393	329	97
PE71S6394	329	98
PE71S6395	328	92
PE71S6396	328	93
PE71S6397	326	88
PE71S6398	326	89
PE71S6399	328	84
PE71S6400	327	32
PE71S6401	329	13
PE71S6402	329	12
PE71S6403	326	97
PE71S6404	327	12
PE71S6405	329	3
PE71S6406	329	94
PE71S6407	329	95
PE71S6408	327	16
PE71S6409	327	20
PE71S6410	327	33
PE71S6413	330	57
PE71S6414	330	58
PE71S6415	330	59
PE71S6416	330	60
PE71S6417	330	62
PE71S6418	330	61
PE71S6419	327	34
PE71S6420	327	35
PE71S6421	327	36
PE71S6422	327	43
PE71S6423	327	52
PE71S6424	327	53
PE71S6425	328	86
PE71S6426	326	83
PE71S6427	327	54
PE71S6428	327	55
PE71S6429	326	3
PE71S6430	327	37
PE71S6431	328	67
PE71S6432	328	74
PE71S6433	327	29
PE71S6434	326	92
PE71S6435	326	84
PE71S6436	326	4
PE71S6437	327	44
PE71S6438	326	85
PE71S6439	328	90
PE71S6440	329	14
PE71S6441	329	15
PE71S6442	329	16
PE71S6443	328	62
PE71S6444	327	61
PE71S6445	329	30
PE71S6446	327	45
PE71S6447	327	46
PE71S6448	329	21
PE71S6449	329	22
PE71S6450	328	65
PE71S6451	328	64
PE71S6452	327	48
PE71S6453	327	49
PE71S6454	327	57
PE71S6455	327	58
PE71S6456	328	69
PE71S6457	328	68
PE71S6458	328	73
PE71S6459	328	72
PE71S6460	326	86
PE71S6461	328	87
PE71S6462	326	91
PE71S6463	326	90
PE71S6464	326	94
PE71S6465	326	95
PE71S6466	326	93
PE71S6467	327	42
PE71S6468	327	38
PE71S6469	327	39
PE71S6470	329	18
PE71S6471	329	17
PE71S6472	327	47
PE71S6473	329	23
PE71S6474	329	24
PE71S6475	329	27
PE71S6476	328	30
PE71S8001	326	81
PE71S8002	326	82
PE71S9001	383	74
PE71S9002	383	75
PE71S9003	383	72
PE71S9004	383	73
PE73SP1000	323	99
PE73SP1001	323	9
PE73SP1002	323	10
PE73SP1003	323	11
PE73SP1004	322	71
PE73SP1005	322	74
PE73SP1006	322	75
PE73SP1007	322	76
PE73SP1008	322	73
PE73SP1010	323	2
PE73SP1011	323	18
PE73SP1013	323	3
PE73SP1014	323	4
PE73SP1015	323	91
PE73SP1016	323	22
PE73SP1017	322	79
PE73SP1018	323	92
PE73SP1019	323	98
PE73SP1021	323	97
PE73SP1022	323	95
PE73SP1023	323	16
PE73SP1024	323	90
PE73SP1025	323	89
PE73SP1026	323	24
PE73SP1027	323	87
PE73SP1028	323	13
PE73SP1029	323	96
PE73SP1030	323	88
PE73SP1031	323	15
PE73SP1032	323	23
PE73SP1033	323	93
PE73SP1034	322	77
PE73SP1035	323	94
PE73SP1036	323	14
PE73SP1037	322	70
PE73SP1038	323	86
PE73SP1039	323	83
PE73SP1040	322	80
PE73SP1041	323	8
PE73SP1042	323	7
PE73SP1048	323	6
PE73SP1049	323	12
PE73SP1050	323	5
PE73SP1051	322	65
PE73SP1060	322	69
PE73SP1061	322	66
PE73SP1062	322	67
PE73SP1063	322	72
PE73SP1064	322	78
PE73SP1065	323	1
PE73SP1066	323	17
PE73SP1067	323	20
PE73SP1068	323	19
PE73SP1069	323	21
PE73SP1070	322	68
PE7AP006-01	74	38
PE7AP006-02	74	38
PE7AP006-03	74	38
PE7AP006-04	74	38
PE7AP006-05	74	38
PE7AP006-06	74	38
PE7AP006-09	74	38
PE7AP006-10	74	38
PE7AP006-12	74	38
PE7AP006-15	74	38
PE7AP006-20	74	38
PE7AP006-30	74	38
PE7AP006-40	74	38
PE7AP1000-0	71	10
PE7AP1000-1	71	10
PE7AP1000-2	71	10
PE7AP1000-3	71	10
PE7AP1000-6	71	10
PE7AP1000-9	71	10
PE7AP1000-12	71	10
PE7AP1000-15	71	10
PE7AP1000-18	71	10
PE7AP1000-20	71	10
PE7AP1001-10	76	53
PE7AP1001-3	76	53
PE7AP1001-6	76	53
PE7AP1001-20	76	53
PE7AP1002-12	71	9
PE7AP1002-15	71	9
PE7AP1002-0	71	9
PE7AP1002-20	71	9
PE7AP1002-1	71	9
PE7AP1002-2	71	9
PE7AP1002-3	71	9
PE7AP1002-6	71	9
PE7AP1002-9	71	9
PE7AP150-03	81	35
PE7AP150-06	81	35
PE7AP150-10	81	35
PE7AP150-20	81	35
PE7AP150-30	81	35
PE7AP150-40	81	35
PE7AP200-20	82	37
PE7AP250-10	82	38
PE7AP250-20	82	38
PE7AP250-30	82	38
PE7AP250-40	82	38
PE7AP402-10	75	43
PE7AP402-20	75	43
PE7AP402-3	75	43
PE7AP402-6	75	43
PE7AP402-30	75	43
PE7AP412-00	70	1
PE7AP412-01	70	1
PE7AP412-02	70	1
PE7AP412-03	70	1
PE7AP412-04	70	3
PE7AP412-05	70	3
PE7AP412-06	70	3
PE7AP412-08	70	3
PE7AP412-09	70	3
PE7AP412-10	70	3
PE7AP412-12	70	3
PE7AP412-15	70	3
PE7AP412-20	70	3
PE7AP412-30	70	3
PE7AP418-03	82	42
PE7AP418-10	82	42
PE7AP418-20	82	42
PE7AP418-30	82	42
PE7AP418-40	82	42
PE7SM1000A	331	65
PE8001	315	1
PE8001-P	315	2
PE8002	315	3
PE8002-P	315	4
PE8003	315	5
PE8003-P	315	6
PE8004-P	315	8
PE8005	315	9
PE8005-P	315	10
PE8006	315	11
PE8006-P	315	12
PE8007	315	13
PE8007-P	315	14
PE8008	315	15
PE8008-P	315	16
PE8009	315	17
PE8009-P	315	18
PE8010	316	28
PE8012	316	29
PE8012P	316	30
PE8013	316	32
PE8014	316	33
PE8015	316	34
PE8016	316	35
PE8017	314	77
PE8018	314	78
PE8019	314	79
PE8020	314	80
PE8021	314	81
PE8022	314	82
PE8023	314	83
PE8024	314	84
PE8025	314	85
PE8026	314	86
PE8027	314	87
PE8028	314	88
PE8029	314	89
PE8030	314	90
PE8031	314	91
PE8032	314	92
PE8033	314	93
PE8034	314	94
PE8035	314	95
PE8036	314	96
PE8037	314	97
PE8040	315	21
PE8044	315	7
PE8203	318	10
PE8210	87	63
PE8211	87	64
PE8212	87	65
PE8213	87	59
PE8214	87	60
PE8215	87	61
PE8216	87	56
PE8217	87	57
PE8218	87	58
PE8219	87	67
PE8220	87	68
PE8221	87	69
PE8222	87	50
PE8223	87	51
PE8224	87	52
PE8225	87	53
PE8226	87	54
PE8227	87	55
PE8231	87	71
PE8232	87	72
PE8233	87	73
PE8234	87	76
PE8236	87	77
PE8237	87	48
PE8239	87	49
PE8240	87	74
PE8242	87	75
PE8243	318	15
PE8244	318	16
PE8245	318	17
PE8246	318	18
PE8247	318	19
PE8250	87	66
PE8251	87	62
PE8252	87	70
PE8253	318	21
PE8255	318	20
PE8258	87	47
PE8300	224	12
PE8301	224	19
PE8302	224	27
PE8303	224	36
PE8304	224	40
PE8305	224	43
PE8306	224	47
PE8310	224	95
PE8311	224	1
PE8312	224	3
PE8313	224	5
PE8314	224	26
PE8315	224	31
PE8316	224	24
PE8317	224	25
PE8318	224	46
PE8319	224	89
PE8320	224	86
PE8321	224	6
PE8322	224	90
PE8323	224	7
PE8324	224	91
PE8325	224	9
PE8326	224	93
PE8327	224	23
PE8328	224	32
PE8400	222	42
PE8401	223	48
PE8402	223	54
PE8403	223	59
PE8404	223	63
PE8405	223	65
PE8406	223	67
PE8410	222	23
PE8411	222	27
PE8412	222	30
PE8413	222	32
PE8414	222	44
PE8415	222	25
PE8416	224	16
PE8417	224	98
PE8418	222	38
PE8419	222	22
PE8420	224	10
PE8421	224	94
PE8422	222	36
PE8423	222	20
PE8424	224	8
PE8425	224	92
PE8426	222	34
PE8427	222	18
PE8428	222	35
PE8429	222	19
PE8430	222	37
PE8431	222	21
PE8432	223	51
PE8433	223	57
PE8501	317	95
PE8503	318	1
PE8504	318	4
PE8505	317	91
PE8506	317	96
PE8507	317	98
PE8508	318	2
PE8509	318	5
PE8600	313	58
PE8601	313	60
PE8602	313	62
PE8603	313	63
PE8650	311	7
PE8652	311	8
PE8653	311	12
PE8654	312	35
PE8700	308	6
PE8701	308	16
PE8702	308	22
PE8703	308	9
PE8704	308	8
PE8705	308	4
PE8706	308	5
PE8707	308	11
PE8708	308	13
PE8709	308	12
PE8710	308	10
PE8711	308	15
PE8712	308	17
PE8713	308	18
PE8714	308	20
PE8715	309	41
PE8716	309	40
PE8717	309	39
PE8718	309	42
PE8719	309	46
PE8720	309	51
PE8721	309	52
PE8722	309	47
PE8723	309	45
PE8724	309	48
PE8725	309	53
PE8726	309	49
PE8727	309	50
PE8729	310	58
PE8730	310	59
PE8731	310	60
PE8732	310	61
PE8733	310	62
PE8734	310	63
PE8735	310	64
PE8736	310	65
PE8738	310	66
PE8739	308	19
PE8740	308	21
PE8741	308	23
PE8742	308	24
PE8743	309	34
PE8747	309	38
PE80L1000	314	65
PE80L1001	314	67
PE80L2000	314	71
PE80L2001	314	68
PE80L2002	314	74
PE80L2003	314	64
PE80L2004	314	72
PE80L2005	314	66
PE80L2006	314	69
PE80L2007	314	75
PE80L2008	314	76
PE80L3000	314	70
PE80L4000	314	73
PE80P1000	316	27
PE80P1001	316	25
PE80P1002	316	26
PE80T1000	316	36
PE80T1001	316	37
PE80T1002	316	38
PE80T1003	316	31
PE80T1004	315	19
PE80T1005	315	20
PE80T3000	377	29
PE80T3001	377	28
PE80T3002	377	27
PE80T3003	377	26
PE80T3004	377	25
PE80T3005	377	24
PE80T4000	315	22
PE80T4001	315	24
PE80T4002	315	23
PE80T6000	316	39
PE80T6001	316	40
PE80T6002	316	41
PE80T6003	316	42
PE80T6004	316	45
PE80T6005	316	46
PE80T6006	317	53
PE80T6007	317	54
PE80T6008	317	59
PE80T6009	317	60
PE80T6010	316	43
PE80T6011	316	44
PE80T6012	316	47
PE80T6013	316	48
PE80T6014	316	49
PE80T6015	316	50
PE80T6016	317	51
PE80T6017	317	52
PE80T6018	317	55
PE80T6019	317	56
PE80T6020	317	57
PE80T6021	317	58
PE80T6022	317	61
PE80T6023	317	62
PE80T6024	317	63
PE80T6025	317	64
PE82P1000	318	14
PE82P2000	319	22
PE82P2001	319	23
PE82P5000	318	12
PE82P5002	318	13
PE82P5003	318	11
PE83CR000	223	58
PE83CR001	222	39
PE83CR002	223	62
PE83CR003	222	41
PE83CR004	223	46
PE83CR005	223	47
PE83CR006	223	53
PE83CR007	222	40
PE83CR1000	222	43
PE83CR1001	222	24
PE83CR1002	222	45
PE83CR1003	222	26
PE83CR1004	223	49
PE83CR1005	222	28
PE83CR1012	223	65
PE83CR1013	222	31
PE83CR1014	223	60
PE83CR1009	222	33
PE83CR1010	223	64
PE83CR1011	223	66
PE83CR1012	223	68
PE83CR1013	222	6
PE83CR1014	222	1
PE83CR1015	222	7
PE83CR1016	222	2
PE83CR1017	222	8
PE83CR1018	222	3
PE83CR1019	222	9
PE83CR1020	222	4
PE83CR1021	222	10
PE83CR1022	222	5
PE83CR1023	222	11
PE83CR1024	222	12
PE83CR1025	222	13
PE83CR1026	223	61
PE83CR1027	222	14
PE83CR1028	222	15
PE83CR1029	222	17
PE83CR1030	223	50
PE83CR1031	222	29
PE83CR1032	222	16
PE83CR1033	223	52
PE83CR1034	223	56
PE83IR000	224	37
PE83IR001	224	41
PE83IR002	224	13
PE83IR003	224	96
PE83IR004	224	18
PE83IR005	224	20
PE83IR006	224	28
PE83IR007	224	11
PE83IR1000	224	15
PE83IR1001	224	97
PE83IR1002	224	17
PE83IR1003	224	99
PE83IR1004	224	21
PE83IR1005	224	2
PE83IR1006	224	30
PE83IR1007	224	4
PE83IR1010A	224	42
PE83IR1011	224	44
PE83IR1012	224	49
PE83IR1013	223	74
PE83IR1014	223	69
PE83IR1015	223	75
PE83IR1016	223	70
PE83IR1017	223	76
PE83IR1018	223	71
PE83IR1019	223	77
PE83IR1020	223	72
PE83IR1021	223	78
PE83IR1022	223	73
PE83IR1023	223	79
PE83IR1024	223	80
PE83IR1025	223	81
PE83IR1026	224	38
PE83IR1027	224	39
PE83IR1028	224	45
PE83IR1029	224	33
PE83IR1030	224	34
PE83IR1031	224	35
PE83IR1032	224	14
PE83IR1033	223	83
PE83IR1034	224	48
PE83IR1035	224	85
PE83IR1036	224	87
PE83IR1037	224	88
PE83IR1038	223	82
PE83IR1039	224	22
PE83IR1040	224	29
PE83IR1041	223	84
PE85N1000	317	68
PE85N1001	317	65
PE85N1002	317	83
PE85N1003	317	84
PE85N1004	317	93
PE85N1005	317	94
PE85N1006	317	87
PE85N1007	317	88
PE85N1008	317	89
PE85N1009	317	90
PE85N1010	317	69
PE85N1011	317	76
PE85N1012	317	79
PE85N1013	317	86
PE85N1014	317	97
PE85N1015	318	99
PE85N1016	318	3
PE85N1017	317	75
PE85N1018	317	80
PE85N1019	317	66
PE85N1020	317	67
PE85N1021	317	85
PE85N1022	317	92
PE85NS4000	317	70
PE85NS4001	317	71
PE85NS4002	317	73
PE85NS4003	317	72
PE85NS4004	317	74
PE85NS5000	317	77
PE85NS5001	317	81
PE85NS5002	317	78
PE85NS5003	317	82
PE86GM2000	312	36
PE86GM2001	312	37
PE86GM2002	312	38
PE86GM2003	312	39
PE86GM2004	312	40
PE86GM2005	312	41
PE86GM2006	312	42
PE86GM2007	312	43
PE86GM2008	312	44
PE86X1000	311	22
PE86X1001	311	25
PE86X1002	311	23
PE86X1003	311	17
PE86X1004	311	20
PE86X1006	311	13
PE86X1007	311	15
PE86X1008	311	14
PE86X1009	311	19
PE86X1010	311	26
PE86X1013	311	94
PE86X1014	311	97
PE86X1015	311	3
PE86X1016	311	98
PE86X1017	311	4
PE86X1018	311	99
PE86

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE9098	44	E3
PE9099	43	C4
PE9100	43	C3
PE9101	30	A4
PE9102	30	C2
PE9103	34	E3
PE9104	39	E3
PE9105	37	A3
PE9106	25	C7
PE9108	41	A7
PE9109	26	A2
PE9111	32	C1
PE9112	33	D2
PE9113	32	B1
PE9114	44	B7
PE9116	41	A2
PE9117	41	B4
PE9118	41	A1
PE9119	41	D4
PE9120	41	C1
PE9122	41	C2
PE9123	32	A3
PE9125	31	C4
PE9126	27	D5
PE9127	31	D1
PE9128	30	C4
PE9129	27	D6
PE9130	31	B7
PE9131	33	D1
PE9132	41	C3
PE9135	41	E2
PE9136	41	D3
PE9137	41	A3
PE9138	41	D6
PE9139	41	E5
PE9140	41	E6
PE9141	41	A6
PE9142	39	E4
PE9143	39	A5
PE9144	37	E3
PE9145	37	A4
PE9146	39	B5
PE9147	39	C5
PE9148	37	B4
PE9149	37	C4
PE9150	26	C2
PE9151	26	B4
PE9152	26	B2
PE9153	26	C4
PE9154	43	C5
PE9155	31	D3
PE9158	26	D4
PE9160	45	A5
PE9163	45	E7
PE9164	45	E5
PE9165	45	A1
PE9166	45	C5
PE9167	45	A2
PE9169	48	C4
PE9171	26	E2
PE9172	25	B7
PE9173	30	A5
PE9174	25	E5
PE9175	48	C3
PE9180	32	B2
PE9181	28	B1
PE9182	34	A7
PE9183	32	C6
PE9184	35	A3
PE9184NH	35	E3
PE9185	38	A5
PE9186	26	D6
PE9187	37	B6
PE9188	40	A2
PE9189	42	B4
PE9191	42	B5
PE9192	42	A4
PE9193	27	A5
PE9194	32	A5
PE9195	43	E3
PE9196	31	E5
PE9198	29	C6
PE9199	48	E2
PE9201	44	D7
PE9204	26	A4
PE9205	27	A4
PE9206	32	B3
PE9207	26	A6
PE9208	26	B6
PE9209	44	D6
PE9210	27	D3
PE9211	28	B4
PE9212	27	E6
PE9213	42	D4
PE9214	38	B3
PE9215	36	C4
PE9216	32	D1
PE9217	30	C7
PE9218	44	C3
PE9219	43	C7
PE9220	22	A3
PE9221	22	E2
PE9223	27	E2
PE9225	33	B6
PE9226	44	A3
PE9227	47	A5
PE9228	47	B5
PE9229	47	B4
PE9230	26	A3
PE9231	26	A5
PE9232	47	E3
PE9234	26	B3
PE9235	47	D5
PE9236	26	B5
PE9237	32	D5
PE9238	32	E3
PE9239	31	C3
PE9240	41	E3
PE9241	41	B3
PE9242	41	A5
PE9243	41	E1
PE9244	47	E4
PE9245	47	B3
PE9246	35	E1
PE9247	34	A6
PE9248	47	C3
PE9249	34	A1

Model No.	Page	C/R
PE9251	40	E3
PE9252	39	C3
PE9253	38	C6
PE9255	38	D6
PE9256	36	C6
PE9257	31	A4
PE9258	32	E4
PE9259	36	A6
PE9260	38	B6
PE9261	32	D3
PE9263	33	C1
PE9264	27	C6
PE9265	28	C5
PE9266	28	A4
PE9267	28	C4
PE9268	28	D4
PE9269	25	C5
PE9270	43	E2
PE9271	47	A3
PE9275	39	D3
PE9276	40	A4
PE9277	32	D6
PE9278	31	D2
PE9280	48	B2
PE9281	41	B6
PE9282	41	B7
PE9283	41	C7
PE9284	41	C6
PE9285	27	C2
PE9286	27	B2
PE9287	43	A6
PE9288	43	B6
PE9290	43	D3
PE9291	44	B3
PE9292	32	E6
PE9293	26	E5
PE9294	26	C6
PE9295	32	B4
PE9296	27	A6
PE9297	28	E3
PE9298	32	E5
PE9299	31	D4
PE9300	26	D5
PE9301	27	A3
PE9302	41	B2
PE9303	41	E4
PE9304	41	B5
PE9305	41	C4
PE9306	46	E3
PE9307	46	D3
PE9308	46	B3
PE9309	41	D1
PE9310	41	B1
PE9311	29	E7
PE9312	35	C3
PE9313	31	D6
PE9314	31	C6
PE9315	32	C7
PE9316	32	B7
PE9317	31	A7
PE9318	31	E6
PE9319	32	E7
PE9320	32	D7
PE9321	22	D1
PE9322	21	D6
PE9323	22	E1
PE9324	21	E6
PE9325	22	B1
PE9326	21	C6
PE9327	38	C3
PE9330	21	B3
PE9332	21	E3
PE9334	42	E3
PE9335	28	B5
PE9336	34	C1
PE9337	34	B1
PE9338	33	E7
PE9339	28	D5
PE9340	28	A5
PE9341	29	C1
PE9342	28	D7
PE9343	28	A7
PE9345	44	E2
PE9346	44	B5
PE9347	28	D6
PE9348	45	C1
PE9349	30	A1
PE9350	30	B2
PE9351	42	A5
PE9352	42	C5
PE9354	42	D5
PE9357	42	B3
PE9358	42	C3
PE9359	30	E3
PE9360	32	B5
PE9361	45	E2
PE9362	45	B3
PE9363	45	C3
PE9364	45	D2
PE9365	45	A3
PE9367	45	D3
PE9368	46	E6
PE9369	46	E4
PE9370	46	D4
PE9371	46	A7
PE9372	44	D5
PE9373	48	A3
PE9374	48	D2
PE9375	48	E1
PE9376	48	C1
PE9377	48	D1
PE9378	48	A2
PE9379	34	E2
PE9380	34	C7
PE9382	30	B6
PE9383	30	D4
PE9384	37	D7
PE9385	33	E2
PE9386	27	B6
PE9387	27	A7
PE9388	31	E2
PE9389	32	D4
PE9390	29	D6
PE9391	46	C3
PE9392	42	C6
PE9393	42	A6
PE9394	42	D6

Model No.	Page	C/R
PE9395	42	B6
PE9396	46	B5
PE9397	46	B7
PE9398	27	D7
PE9399	40	B2
PE9400	37	E7
PE9401	37	D6
PE9402	40	C2
PE9403	33	D5
PE9404	33	C6
PE9405	33	A6
PE9406	26	D2
PE9407	38	B5
PE9408	39	B4
PE9409	23	E6
PE9411	36	D4
PE9413	28	C1
PE9414	23	C7
PE9415	40	B4
PE9416	46	B4
PE9417	46	A4
PE9418	34	D2
PE9419	27	E7
PE9420	25	E6
PE9421	45	E1
PE9429	30	B5
PE9431	37	A2
PE9432	39	B3
PE9433	37	D2
PE9434	39	A4
PE9435	39	C4
PE9436	19	C7
PE9437	19	E7
PE9438	20	C1
PE9439	37	A7
PE9440	40	B3
PE9442	40	D3
PE9443	43	A3
PE9444	43	E4
PE9445	43	D1
PE9446	31	C7
PE9449	33	E1
PE9450	33	C2
PE9451	18	D7
PE9452	18	E7
PE9453	19	C1
PE9454	20	D6
PE9455	20	E3
PE9456	20	A7
PE9457	20	C3
PE9458	19	C3
PE9460	20	A5
PE9461	21	A1
PE9462	32	B6
PE9463	32	A6
PE9464	31	A5
PE9465	31	E4
PE9466	28	B3
PE9467	28	E2
PE9468	28	A3
PE9469	28	D2
PE9470	38	A7
PE9471	38	E6
PE9472	36	E6
PE9473	36	D6
PE9474	28	B2
PE9475	39	B1
PE9476	37	A1
PE9477	39	C1
PE9478	37	B1
PE9479	28	E1
PE9480	29	A2
PE9481	30	E1
PE9482	33	B2
PE9484	25	A6
PE9485	35	D1
PE9486	39	D3
PE9487	37	E2
PE9488	37	C3
PE9489	31	E1
PE9490	32	D2
PE9491	31	C2
PE9492	32	C3
PE9493	36	A5
PE9494	38	C4
PE9495	36	C5
PE9496	38	E4
PE9497	37	B3
PE9498	39	E2
PE9499	37	B2
PE9500	30	A6
PE9501	19	A4
PE9502	19	A6
PE9503	19	E5
PE9504	19	E3
PE9505	34	A2
PE9506	34	A4
PE9507	34	D7
PE9508	35	C2
PE9511	37	C5
PE9512	39	E6
PE9513	37	A6
PE9516	29	D3
PE9517	29	E2
PE9518	29	C3
PE9520	28	C3
PE9521	44	A5
PE9522	29	C2
PE9523	29	B2
PE9524	28	A2
PE9525	29	B3
PE9526	29	A4
PE9527	29	A3
PE9528	29	E3
PE9529	26	A1
PE9530	25	E7
PE9531	43	E6
PE9532	43	D6
PE9533	35	D5
PE9534	35	B5
PE9535	31	A1
PE9536	26	E1
PE9537	26	E3
PE9538	31	A3
PE9539	32	C4
PE9540	32	A4
PE9541	30	E4

Model No.	Page	C/R
PE9542	44	D2
PE9543	44	C2
PE9544	44	E4
PE9545	44	D4
PE9546	34	B4
PE9547	30	B1
PE9548	30	B4
PE9550	31	E7
PE9551	39	C2
PE9552	33	A2
PE9553	32	C5
PE9554	31	B4
PE9556	23	A7
PE9557	23	A6
PE9558	24	E2
PE9559	24	C6
PE9560	43	E1
PE9561	43	B3
PE9562	44	C1
PE9563	44	B2
PE9564	44	B4
PE9565	31	A2
PE9566	32	E2
PE9567	27	C5
PE9568	33	A7
PE9569	27	C7
PE9570	31	D5
PE9571	33	B7
PE9572	33	E5
PE9573	33	D6
PE9574	27	E4
PE9575	27	C4
PE9576	27	E3
PE9577	27	D3
PE9578	27	B4
PE9579	27	E5
PE9580	27	D4
PE9581	40	A5
PE9582	46	A6
PE9583	47	C1
PE9584	46	E5
PE9585	47	B1
PE9586	46	B6
PE9587	47	E1
PE9589	47	D1
PE9593	36	A1
PE9594	35	C7
PE9595	30	A2
PE9596	40	B6
PE9597	40	A6
PE9598	40	D6
PE9599	40	E6
PE9600	40	B5
PE9602	40	C5
PE9603	40	D5
PE9604	40	B7
PE9605	40	A7
PE9606	40	D7
PE9607	40	C7
PE9608	46	D1
PE9609	46	B1
PE9610	46	C1
PE9611	46	E1
PE9612	46	C5
PE9613	46	E7
PE9614	46	D5
PE9615	47	A1
PE9616	46	B2
PE9617	46	C2
PE9618	46	D2
PE9619	46	E2
PE9620	35	D2
PE9621	34	B6
PE9622	47	B6
PE9623	47	A6
PE9624	47	D6
PE9625	47	C6
PE9626	46	C6
PE9627	46	D6
PE9628	47	A2
PE9629	47	B2
PE9630	47	D7
PE9631	47	A7
PE9632	45	A7
PE9633	45	E6
PE9634	45	D7
PE9638	43	D7
PE9640	19	E1
PE9642	34	B3
PE9647	20	E1
PE9648	20	B2
PE9649	21	D5
PE9650	21	B7
PE9651	21	A6
PE9652	21	D7
PE9653	36	B3
PE9654	36	C3
PE9655	38	A2
PE9656	38	B2
PE9658	21	B6
PE9659	22	A1
PE9660	20	C7
PE9661	20	E5
PE9662	20	A6
PE9663	21	E1
PE9664	21	A2
PE9665	20	B6
PE9666	20	A3
PE9667	20	E2
PE9669	34	C3
PE9670	35	D3
PE9672	19	C2
PE9673	19	B4
PE9674	19	E2
PE9675	19	D4
PE9676	21	C4
PE9678	21	B4
PE9680	47	D2
PE9682	36	E1
PE9683	36	A2
PE9684	39	B2
PE9685	42	D3
PE9687	26	B7
PE9688	26	A7
PE9689	26	C7
PE9690	36	D2
PE9691	38	B1

Model No.	Page	C/R
PE9692	36	C2
PE9693	38	C1
PE9694	34	C4
PE9695	34	E7
PE9696	26	E7
PE9697	27	B1
PE9698	27	C1
PE9699	44	D1
PE9700	44	E1
PE9701	45	B1
PE9703	38	E5
PE9704	31	E3
PE9705	28	E7
PE9706	29	A1
PE9707	36	E5
PE9708	38	A6
PE9709	29	B1
PE9710	29	D1
PE9711	27	D1
PE9712	27	E1
PE9713	44	A2
PE9714	44	C4
PE9715	18	D3
PE9716	18	B3
PE9718	18	D5
PE9719	18	E5
PE9720	18	A7
PE9721	18	B7
PE9722	36	A4
PE9724	38	E2
PE9725	38	A3
PE9726	38	D1
PE9727	36	E2
PE9728	36	A3
PE9729	38	E1
PE9730	33	B3
PE9731	33	C3
PE9732	40	E5
PE9733	40	C6
PE9734	45	A6
PE9735	47	C4
PE9736	47	A4
PE9738	46	A5
PE9739	46	C7
PE9740	46	D7
PE9741	45	B7
PE9742	45	C6
PE9743	45	D6
PE9744	45	C7
PE9745	21	B5
PE9746	21	A5
PE9747	18	C5
PE9748	21	A7
PE9749	33	D7
PE9750	25	B2
PE9751	25	D1
PE9752	25	C2
PE9753	25	E1
PE9754	25	D2
PE9755	25	A2
PE9756	25	A1
PE9757	25	B1
PE9758	25	B5
PE9759	45	B5
PE9760	45	E4
PE9768	21	C2
PE9770	30	E5
PE9771	30	D6
PE9773	30	A7
PE9774	34	D4
PE9775	42	A2
PE9776	42	A1
PE9777	42	B2
PE9778	39	A7
PE9779	40	E1
PE9780	28	A6
PE9782	21	D1
PE9783	44	B1
PE9786	39	D4
PE9787	31	C5
PE9791	45	E3
PE9801	366	6
PE9802	366	17
PE9803	366	70
PE9804	366	8
PE9805	366	15
PE9806	366	71
PE9809	366	64
PE9810	366	9
PE9811	366	16
PE9812	365	55
PE9813A	365	54
PE9819	366	82
PE9820	367	34
PE9821	367	58
PE9822	367	70
PE9823	367	76
PE9824	368	85
PE9826	365	39
PE9827	365	43
PE9828	365	59
PE9830	367	52
PE9831	367	59
PE9832	367	71
PE9833	367	77
PE9834	367	80
PE9835	368	93
PE9837	367	33
PE9838	367	53
PE9839	367	60
PE9840	367	72
PE9842	368	86
PE9843	368	94
PE9846	366	74
PE9847	366	84
PE9848	366	10
PE9850B/2F-10	360	1
PE9850B-10	361	75
PE9850B/2F-15	360	2
PE9850B-15	361	76
PE9850B/2F-20	360	3
PE9850B-20	361	77
PE9851B/2F-10	360	4
PE9851B-10	361	78
PE9851B/2F-15	360	5
PE9851B-15	361	79
PE9851B/2F-20	360	6

Model No.	Page	C/R
PE9851B-20	361	80
PE9852B/2F-10	360	7
PE9852B-10	361	81
PE9852B/2F-15	360	8
PE9852B-15	361	82
PE9852B/2F-20	360	9
PE9852B-20	361	83
PE9853B/SF-10	360	10
PE9853B-10	361	84
PE9853B/SF-15	360	11
PE9853B-15	361	85
PE9853B-20	361	86
PE9854B/NF-10	360	12
PE9854B/SF-10	360	15
PE9854B-10	361	87
PE9854B/NF-15	360	13
PE9854B/SF-15	360	16
PE9854B-15	361	88
PE9854B/NF-20	360	14
PE9854B/SF-20	360	17
PE9854B-20	361	89
PE9855B/NF-10	360	19
PE9855B/SF-10	360	21
PE9855B-10	361	90
PE9855B/NF-15	360	18
PE9855B/SF-15	360	20
PE9855B-15	361	91
PE9855B/NF-20	360	19
PE9855B/SF-20	360	21
PE9855B-20	361	92
PE9856B/NF-10	360	22
PE9856B/SF-10	360	25
PE9856B-10	361	93
PE9856B/NF-15	360	23
PE9856B/SF-15	360	26
PE9856B-15	361	94
PE9856B/NF-20	360	24
PE9856B/SF-20	360	27
PE9856B-20	361	95
PE9857B/NF-10	360	28
PE9857B/SF-10	360	30
PE9857B-10	361	96
PE9857B/NF-15	360	28
PE9857B/SF-15	360	30
PE9857B-15	361	97
PE9857B/NF-20	360	29
PE9857B/SF-20	360	31
PE9857B-20	361	98
PE9858B/NF-10	360	32
PE9858B/SF-10	360	34
PE9858B-10	361	99
PE9858B/NF-15	360	32
PE9858B/SF-15	360	34
PE9858B-15	361	1
PE9858B/NF-20	360	33
PE9858B/SF-20	360	35
PE9858B-20	361	2
PE9859B/NF-10	360	36
PE9859B/SF-10	360	38
PE9859B-10	361	4
PE9859B/NF-15	360	37
PE9859B/SF-15	360	39
PE9859B-15	361	5
PE9859B-20	361	3
PE9860B-10	362	7
PE9860B/NF-15	360	40
PE9860B/SF-15	360	41
PE9860B-15	362	8
PE9860B-20	361	6
PE9861B-10	362	9
PE9862B-15	362	11
PE9862B-20	362	10
PE9863B/NF-10	360	42
PE9863B/SF-10	360	43
PE9863B-10	362	15
PE9863B-10-U	362	16
PE9863B-15	362	12
PE9863B-15-U	362	13
PE9863B-20-U	362	14
PE9864B/NF-10	360	44
PE9864B/SF-10	360	45
PE9864B-10	362	17
PE9864B/NF-15	360	44
PE9864B/SF-15	360	45
PE9865	367	37
PE9866	366	72
PE9867	366	83
PE9868	366	94
PE9869	366	12
PE9870	367	35
PE9871	368	19
PE9872	368	92
PE9873	366	5
PE9874	366	81
PE9875	366	73
PE9876	367	51
PE9877	367	78
PE9878	365	53
PE9879	365	60
PE9881A-20	365	17
PE9881-24	361	69
PE9881-34	365	19
PE9881-42	365	16
PE9884	367	36
PE9887-11	365	14
PE9888-11	365	15
PE9889	366	7
PE9890	366	18
PE9918	43	A7
PE91002	38	D5
PE91003	36	D5
PE91005	40	C4
PE91006	40	D4
PE91007	38	A1
PE91008	36	E3
PE91009	38	C2
PE91010	36	D3
PE91011	38	D2
PE91027	23	C5
PE91028	23	D5
PE91029	23	D6
PE91030	30	E7
PE91031	32	E1
PE91032	31	B1
PE91033	32	A2
PE91034	29	A6
PE91036	38	D3

Model No.	Page	C/R
PE91038	23	B7
PE91039	23	E4
PE91040	29	B7
PE91042	38	A4
PE91044	26	C3
PE91045	38	C5
PE91046	42	E4
PE91048	19	B6
PE91049	39	B6
PE91050	39	C6
PE91051	39	A1
PE91052	36	C7
PE91054	39	B7
PE91055	19	C6
PE91056	39	D6
PE91057	39	C7
PE91058	39	D7
PE91059	40	B1
PE91060	21	B2
PE91061	39	E7
PE91062	37	E5
PE91063	37	B5
PE91064	40	D1
PE91065	42	E2
PE91066	40	A1
PE91068	42	B1
PE91069	28	B6
PE91070	20	A4
PE91072	42	C1
PE91073	44	C5
PE91080	47	C7
PE91081	47	B7
PE91082	48	A1
PE91083	47	E7
PE91084	18	E3
PE91085	18	A3
PE91086	18	C3
PE91087	44	A6
PE91088	24	D1
PE91090	24	C4
PE91091	24	A5
PE91092	22	A5
PE91093	22	D5
PE91094	22	B6
PE91095	22	E6
PE91099	42	D1
PE91101	42	E1
PE91102	41	E7
PE91103	36	E7
PE91104	26	D1
PE91105	48	D5
PE91106	48	B5
PE91107	48	C5
PE91108	18	B2
PE91109	18	D2
PE91111	19	A5
PE91113	20	A2
PE91114	29	C7
PE91115	18	A4
PE91117	23	E5
PE91118	18	A2
PE91119	18	C2
PE91121	19	D3
PE91122	19	C5
PE91123	19	D5
PE91124	20	B5
PE91125	20	C5
PE91126	20	D5
PE91127	21	B1
PE91128	21	C1
PE91129	38	D7
PE91134	31	C1
PE91135	34	E1
PE91138	19	A1
PE91140	30	B3
PE91141	30	C3
PE91144	21	E2
PE91145	19	E6
PE91146	19	A7
PE91147	22	C2
PE91148	22	B2
PE91151	34	A3
PE91153	35	C1
PE91155	34	B5
PE91157	18	C4
PE91161	18	A5
PE91162	18	B6
PE91163	18	D6
PE91165	20	B4
PE91167	20	D7
PE91168	20	D4
PE91169	21	C3
PE91172	42	E7
PE91173	43	D2
PE91174	43	D4
PE91175	38	E3
PE91176	35	C4
PE91177	31	A6
PE91178	32	A7
PE91179	30	E5
PE91190	23	C4
PE91191	23	A5
PE91192	23	B6
PE91193	23	D7
PE91194	22	C3
PE91195	22	E3
PE91197	22	B4
PE91198	29	C5
PE91199	29	E6
PE91200	30	D2
PE91201	30	C5
PE91202	43	A1
PE91203	43	A2
PE91204	43	A4
PE91205	43	D5
PE91206	24	B1
PE91207	24	E1
PE91208	24	D4
PE91209	24	A4
PE91211	24	A3
PE91212	24	C3
PE91213	24	A7
PE91214	24	D6
PE91215	24	C7
PE91216	22	E4
PE91217	22	B5
PE91218	22	C6

Model No.	Page	C/R
PE91219	22	E5
PE91222	34	C5
PE91227	23	D4
PE91228	23	B5
PE91229	23	C6
PE91230	23	E7
PE91231	22	D3
PE91233	22	A4
PE91234	22	C4
PE91235	29	D5
PE91236	29	A7
PE91237	30	E2
PE91238	30	D5
PE91239	43	B1
PE91240	43	B2
PE91241	43	B4
PE91242	43	E5
PE91243	24	C1
PE91244	24	A2
PE91245	24	E4
PE91246	24	B4
PE91247	24	B5
PE91248	24	B3
PE91249	24	D3
PE91250	24	B7
PE91251	24	E6
PE91252	24	D7
PE91254	22	C5
PE91255	22	D6
PE91256	22	A6
PE91258	35	B2
PE91259	35	E4
PE91260	35	E5
PE91261	35	D6
PE91262	35	D7
PE91263	35	C6
PE91264	35	C5
PE91265	35	A5
PE91266	35	A6
PE91267	35	B6
PE91268	35	A7
PE91269	36	C1
PE91270	36	B1
PE91290	35	A4
PE91291	21	C7
PE91294	21	C5
PE91298	20	B3
PE91299	38	B7
PE91300	38	C7
PE91301	38	E7
PE91302	36	A7
PE91303	36	B7
PE91304	36	D7
PE91305	39	D5
PE91306	39	E5
PE91307	39	A6
PE91308	40	C1
PE91309	37	D4
PE91310	37	E4
PE91311	37	A5
PE91312	37	D5
PE91321	34	D6
PE91324	45	B4
PE91328	44	E7
PE91329	45	D1
PE91330	35	E6
PE91331	35	B

PART NUMBER INDEX

Note: C/R stands for the Column and/or Row location of the specific product on a given page.

Model No.	Page	C/R
PE91463	18	D1
PE91464	23	B1
PE91465	22	D7
PE91466	22	B7
PE91467	22	E7
PE91468	24	B2
PE91469	24	C2
PE91470	24	C5
PE91471	24	A6
PE91472	24	D5
PE91473	24	B6
PE91474	23	B2
PE91475	23	E3
PE91476	23	E1
PE91477	23	C2
PE91478	23	D2
PE91479	23	C3
PE91480	23	A2
PE91481	23	D3
PE91482	23	A4
PE91483	23	E2
PE91484	23	B3
PE91487	44	C6
PE91492	34	E4
PE91493	34	A5
PE91494	35	A1
PE91495	35	B1
PE91496	34	B2
PE91497	34	C2
PE91498	19	B1
PE91499	20	E6
PE91502	19	B3
PE91503	20	A1
PE91504	34	E6
PE91505	43	C2
PE91506	33	B1
PE91507	37	C7
PE91508	19	A3
PE91510	20	B1
PE91511	18	E4
PE91512	18	C6
PE91513	18	E6
PE91514	20	E4
PE91515	21	D3
PE91516	19	D7
PE91517	20	D1
PE91518	18	D4
PE91519	18	B5
PE91520	20	B7
PE91521	20	E7
PE91522	20	C4
PE91523	21	A4
PE91525	19	B5
PE91526	19	E4
PE91528	21	D4
PE91529	19	A2
PE91530	30	D3
PE91531	29	D7
PE91532	29	B6
PE91534	18	A6
PE91535	34	D3
PE91536	36	B4
PE91537	32	A1
PE91538	20	C2
PE91540	19	D2
PE91542	19	C4
PE91546	22	C1
PE91547	21	E7
PE91549	35	B4
PECX001	228	81
PECX002	228	82
PECX003	228	83
PECX004	229	84
PECX005	229	85
PECX006	229	86
PECX007	229	87
PECX008	229	88
PEHFL0000	308	
PEHFL0000	308	
PETP1001	342	86
PETP1002	342	87
PETP1003	342	88
PETP1004	342	90
PETP1005	342	91
PETP1006	342	93
PETP1007	342	94
PETP1008	342	95
PETP1009	342	96
PETP1010	342	98
PETP1012	342	3
PETP1013	342	4
PETP1014	342	6
PETP1015	342	7
PETP1016	342	9
PETP1017	342	10
PEW05S000-1	383	81
PEW05S000-12	383	85
PEW05S000-3	383	82
PEW05S000-6	383	83
PEW05S000-9	383	84
PEW06S000-1	383	86
PEW06S000-12	383	90
PEW06S000-3	383	87
PEW06S000-6	383	88
PEW06S000-9	383	89
PEW08S000-1	383	91
PEW08S000-12	384	95
PEW08S000-3	383	92
PEW08S000-6	383	93
PEW08S000-9	384	94
PEW10CP010-20	371	8
PEW10FS2	388	13
PEW10S010-3	384	96
PEW10S010-6	384	97
PEW10SP4	388	14
PEW10TR0001	385	81
PEW112FS5	389	57
PEW112SP5	389	58
PEW12FS2	388	15
PEW12S010-3	384	98
PEW12S010-6	384	99
PEW12S010-9	384	2
PEW12SP4	388	16
PEW12TW001	387	76
PEW137FS7	389	65
PEW137SP7	389	66
PEW159FS7	389	67
PEW159SP7	389	68
PEW15A001	365	18
PEW15FS2	388	17
PEW15S010-12	384	8
PEW15SP4	388	18
PEW15TR0001	385	84
PEW187FS7	389	69
PEW187SP7	389	70
PEW19FS3	388	19
PEW19S010-12	384	14
PEW19S010-3	384	10
PEW19SP4	388	20
PEW19TR0001	385	85
PEW22B100	369	42
PEW22B101	369	43
PEW22CA100	365	30
PEW22CP010-20	371	21
PEW22FS3	388	21
PEW22S010-3	384	17
PEW22SP4	388	22
PEW22TW001	387	86
PEW284FS8	389	71
PEW284SP8	389	72
PEW28CP010-20	372	25
PEW28FS3	388	25
PEW28S010-3	384	22
PEW28S010-6	384	23
PEW28SP4	388	26
PEW28TW001	387	88
PEW340FS10	389	73
PEW340SP10	389	74
PEW34FS4	388	27
PEW34SP4	388	28
PEW42B100	370	47
PEW42B101	370	48
PEW42FS4	388	29
PEW42SP4	388	30
PEW430FS10	389	75
PEW430SP10	389	76
PEW5B0000	369	27
PEW5B0001	369	28
PEW5TW0000	387	4
PEW5TW0001	387	5
PEW5TW0002	387	6
PEW62FS5	388	37
PEW62SP5	388	38
PEW6B0000	369	29
PEW6B0001	369	30
PEW6TW0000	387	1
PEW6TW0001	387	2
PEW6TW0002	387	3
PEW75FS5	388	41
PEW75SP5	388	42
PEW8B0000	369	31
PEW8B0001	369	32
PEW8TW0000	387	97
PEW8TW0001	387	98
PEW8TW0002	387	99
PEW90FS5	389	49
PEW90SP5	389	50
PEWAD5000	370	72
PEWAD5001	370	73
PEWAD5002	370	74
PEWAD5003	370	75
PEWAD5004	370	77
PEWAD5005	370	79
PEWAD5006	370	82
PEWAD5007A	370	76
PEWAD5008	370	78
PEWAD5009	370	80
PEWAD5010	370	81
PEWAD5011	370	83
PEWAD5012	370	84
PEWAD5013	370	85
PEWAD5014	370	86
PEWAD5015	370	87
PEWAD5016	370	88
PEWAD5017	370	89
PEWAD5018	370	90
PEWAD5019	370	91
PEWAM0000	389	77
PEWAM0001	389	78
PEWAM0002	389	79
PEWAM0003	389	80
PEWAN1005	361	71
PEWAN1006	361	72
PEWAN1007	361	73
PEWAN1008	361	74
PEWAN1009	361	66
PEWAN1010	361	67
PEWAN1011	361	68
PEWAN1012	361	70
PEWAN1013	361	62
PEWAN1014	361	63
PEWAN1015	361	64
PEWAN1016	361	65
PEWAN1017	361	58
PEWAN1018	361	59
PEWAN1019	361	60
PEWAN1020	361	61
PEWAN1021	361	54
PEWAN1022	361	55
PEWAN1023	361	56
PEWAN1024	361	57
PEWAN1025	361	50
PEWAN1026	361	51
PEWAN1027	361	52
PEWAN1028	361	53
PEWAN1029	361	46
PEWAN1030	361	47
PEWAN1031	361	48
PEWAN1032	361	49
PEWAN1033	362	50
PEWAN1034	362	51
PEWAN1035	362	52
PEWAN1036	362	53
PEWAN1037	362	46
PEWAN1038	362	47
PEWAN1039	362	48
PEWAN1040	362	49
PEWAN1041	362	42
PEWAN1042	362	43
PEWAN1043	362	44
PEWAN1044	362	45
PEWAN1045	362	38
PEWAN1046	362	39
PEWAN1047	362	40
PEWAN1048	362	41
PEWAN1049	362	30
PEWAN1050	362	31
PEWAN1051	362	32
PEWAN1052	362	33
PEWAN1053	362	34
PEWAN1054	362	35
PEWAN1055	362	36
PEWAN1056	362	37
PEWAN1057	362	26
PEWAN1058	362	27
PEWAN1059	362	28
PEWAN1060	362	29
PEWAN1061	362	22
PEWAN1062	362	23
PEWAN1063	362	24
PEWAN1064	362	25
PEWAN1065	362	18
PEWAN1066	362	19
PEWAN1067	362	20
PEWAN1068	362	21
PEWAN1069	363	58
PEWAN1070	363	59
PEWAN1071	363	56
PEWAN1072	363	57
PEWAN1073	363	54
PEWAN1074	363	55
PEWAN1075	363	70
PEWAN1076	363	72
PEWAN1077	363	71
PEWAN1078	363	73
PEWAN1079	363	66
PEWAN1080	363	68
PEWAN1081	363	67
PEWAN1082	363	60
PEWAN1083	363	69
PEWAN1084	363	62
PEWAN1085	363	61
PEWAN1086	363	63
PEWAN1087	363	79
PEWAN1088	363	77
PEWAN1089	363	76
PEWAN1101	363	64
PEWAN1102	363	65
PEWAN1109	364	92
PEWAN1110	364	13
PEWAN1111	364	11
PEWAN1112	364	12
PEWAN1113	364	9
PEWAN1114	364	8
PEWAN1115	364	7
PEWAN1116	364	5
PEWAN1117	364	4
PEWAN1118	364	2
PEWAN1119	364	99
PEWAN1120	364	98
PEWAN1121	364	95
PEWAN1122	364	94
PEWAN1123	364	93
PEWAN1124	363	81
PEWAN1125	363	82
PEWAN1126	363	83
PEWAN1127	364	84
PEWAN1128	364	85
PEWAN1129	364	86
PEWAN1130	364	87
PEWAN1131	364	88
PEWAN1132	364	89
PEWAN1133	363	80
PEWAN1134	363	78
PEWAN1135	363	74
PEWAN1136	363	75
PEWAN1137	364	96
PEWAN1138	364	1
PEWAN1139	364	3
PEWAN1140	364	6
PEWAN1141	364	97
PEWAN1142	364	10
PEWAN1143	364	91
PEWAN1144	364	90
PEWAT1007-10	379	54
PEWAT1007-20	379	55
PEWAT1007-3	379	52
PEWAT1007-30	379	56
PEWAT1007-6	379	53
PEWAT1008-10	379	49
PEWAT1008-20	379	50
PEWAT1008-3	379	47
PEWAT1008-30	379	51
PEWAT1008-6	379	48
PEWAT1009-10	379	44
PEWAT1009-20	379	45
PEWAT1009-3	379	42
PEWAT1009-30	379	46
PEWAT1009-6	379	43
PEWAT1010-10	379	39
PEWAT1010-20	379	40
PEWAT1010-3	379	37
PEWAT1010-30	379	41
PEWAT1010-6	379	38
PEWAT1011-10	379	34
PEWAT1011-20	379	35
PEWAT1011-3	379	32
PEWAT1011-30	379	36
PEWAT1011-6	379	33
PEWAT1012-10	379	29
PEWAT1012-20	379	30
PEWAT1012-3	379	27
PEWAT1012-30	379	31
PEWAT1012-6	379	28
PEWCA1000	365	36
PEWCA1001	365	41
PEWCA1002A	365	57
PEWCA1003	366	67
PEWCA1004	366	77
PEWCA1005	366	75
PEWCA1006	366	1
PEWCA1007	366	93
PEWCA1008	366	99
PEWCA1009	366	91
PEWCA1010	367	32
PEWCA1011	367	28
PEWCA1012	367	31
PEWCA1013	367	26
PEWCA1014	367	48
PEWCA1015	367	46
PEWCA1016	367	47
PEWCA1017	367	44
PEWCA1018	365	47
PEWCA1019	365	48
PEWCA1020	365	37
PEWCA1021	365	42
PEWCA1022	365	52
PEWCA1023	366	66
PEWCA1024	366	78
PEWCA1025	366	97
PEWCA1026	365	46
PEWCA1027	365	58
PEWCA1028	366	65
PEWCA1029	366	76
PEWCA1030	366	98
PEWCA1031	366	95
PEWCA1032	366	88
PEWCA1033	366	87
PEWCA1034	366	92
PEWCA1035	366	89
PEWCA1036	366	90
PEWCA1037	366	11
PEWCA1038	366	13
PEWCA1039	366	14
PEWCA1040	367	30
PEWCA1041	367	29
PEWCA1042	367	24
PEWCA1043	367	23
PEWCA1044	367	27
PEWCA1045	367	25
PEWCA1046	367	50
PEWCA1047	367	49
PEWCA1048	367	42
PEWCA1049	367	41
PEWCA1050	367	45
PEWCA1051	367	43
PEWCA1052	367	55
PEWCA1053	367	54
PEWCA1054	367	57
PEWCA1055	367	56
PEWCA1056	367	69
PEWCA1057	367	67
PEWCA1058	367	66
PEWCA1059	367	68
PEWCA1060	367	73
PEWCA1061	367	75
PEWCA1062	367	74
PEWCA1063	367	82
PEWCA1064	367	79
PEWCA1065	367	81
PEWCA1066	368	88
PEWCA1067	368	89
PEWCA1068	368	90
PEWCA1069	368	91
PEWCA1070	365	51
PEWCA1071	366	69
PEWCA1072	366	68
PEWCA1073	366	80
PEWCA1074	366	79
PEWCA1075	366	96
PEWCA1076	367	65
PEWCA1077	368	87
PEWCA1078	365	32
PEWCA1079	368	95
PEWCA1080	368	96
PEWCA1081	368	83
PEWCA1082	368	84
PEWCA1083	367	63
PEWCA1084	367	62
PEWCA1085	367	61
PEWCA1086	367	39
PEWCA1087	367	38
PEWCA1088	367	40
PEWCA1089	366	20
PEWCA1090	366	21
PEWCA1092	366	2
PEWCA1093	366	3
PEWCA1095	366	85
PEWCA1096	366	86
PEWCA1097	365	61
PEWCA1098	366	62
PEWCA1099	365	56
PEWCA1100	365	45
PEWCA1101	365	44
PEWCA1102	365	40
PEWCA1103	365	33
PEWCA1104	365	34
PEWCA1105	367	64
PEWCA1106	366	22
PEWCA1107	366	4
PEWCA1108	366	63
PEWCA1109	365	38
PEWCA1110	365	31
PEWCA1111	368	99
PEWCA1112	368	2
PEWCA1113	368	4
PEWCA1114	368	6
PEWCA1115	368	98
PEWCA1116	368	1
PEWCA1117	368	3
PEWCA1118	368	5
PEWCA1119	368	7
PEWCA1120	368	97
PEWCP1005	372	31
PEWCP1006	372	29
PEWCP1007	372	30
PEWCP1008	372	35
PEWCP1009	372	36
PEWCP1010	372	37
PEWCP1011	372	38
PEWCP1012	372	39
PEWCP1013	372	40
PEWCP1014	372	41
PEWCP1015	372	42
PEWCP1016	372	43
PEWCP1017	372	44
PEWCP1018	372	46
PEWCP1019	372	48
PEWCP1020	372	45
PEWCP1021	372	47
PEWCP1022	372	49
PEWCP1023A	372	50
PEWCP1024	372	52
PEWCP1025	372	54
PEWCP1026	372	51
PEWCP1027	372	53
PEWCP1028	372	55
PEWCP1029	372	56
PEWCP1030	372	58
PEWCP1031	372	60
PEWCP1032	372	57
PEWCP1033	372	59
PEWCP1034	372	61
PEWCP1035	372	62
PEWCP1036	372	63
PEWCP1037	372	64
PEWCP1038	372	65
PEWCP1039	372	66
PEWCP1040	372	67
PEWCP1041	372	68
PEWCP1042	372	69
PEWCP1043	373	70
PEWCP1044	373	71
PEWCP1045	373	72
PEWCP1046	373	73
PEWCP1047	373	74
PEWCP1048	373	75
PEWCP1049	373	76
PEWCP1050	373	77
PEWCP1051	373	79
PEWCP1052A	373	80
PEWCP1053	373	81
PEWCP1054	373	78
PEWCP1055	373	82
PEWCP1056	373	84
PEWCP1057	373	86
PEWCP1058	373	88
PEWCP1059	373	83
PEWCP1060	373	85
PEWCP1061	373	87
PEWCP1062	373	89
PEWCP1063	373	90
PEWCP1064	373	92
PEWCP1065	373	94
PEWCP1066	373	96
PEWCP1067	373	91
PEWCP1068	373	93
PEWCP1069	373	95
PEWCP1070	373	97
PEWCP1071	373	98
PEWCP1072	373	1
PEWCP1073	373	3
PEWCP1074	373	5
PEWCP1075	373	99
PEWCP1076	373	2
PEWCP1077	373	4
PEWCP1078	373	6
PEWCP1079-10	371	23
PEWCP1080-20	371	13
PEWCT1000	373	7
PEWCT1001	373	8
PEWCT1002	373	9
PEWCT1003	373	10
PEWCT1004	373	11
PEWCT1005	373	12
PEWCT1006	373	13
PEWCT1007	373	14
PEWCT1008	374	15
PEWCT1009	374	16
PEWCT1010	374	17
PEWCT1011	374	18
PEWCT1012	374	19
PEWCT1013	374	20
PEWCT1014	374	21
PEWCT1015	374	22
PEWCT1016	374	24
PEWCT1017	374	25
PEWCT1018	374	26
PEWCT1019	374	23
PEWCT1020	374	27
PEWCT1021	374	29
PEWCT1022	374	31
PEWCT1023	374	33
PEWCT1024	374	28
PEWCT1025	374	30
PEWCT1026	374	32
PEWCT1027	374	34
PEWCT1028	374	35
PEWCT1029	374	37
PEWCT1030	374	39
PEWCT1031	374	41
PEWCT1032	374	36
PEWCT1033	374	38
PEWCT1034	374	40
PEWCT1035	374	42
PEWCT1036	374	43
PEWCT1037	374	45
PEWCT1038	374	47
PEWCT1039	374	49
PEWCT1040	374	44
PEWCT1041	374	46
PEWCT1042	374	48
PEWCT1043	374	50
PEWCT1044	374	51
PEWCT1045	374	52
PEWCT1046	374	53
PEWCT1047	374	54
PEWCT1048	374	55
PEWCT1049	374	56
PEWCT1050	374	57
PEWCT1051	374	58
PEWCT1052	375	59
PEWCT1053	375	60
PEWCT1054	375	61
PEWCT1055	375	62
PEWCT1056	375	63
PEWCT1057	375	64
PEWCT1058	375	65
PEWCT1059	375	66
PEWCT1060	375	70
PEWCT1061	375	72
PEWCT1062	375	74
PEWCT1063	375	68
PEWCT1064	375	71
PEWCT1065	375	73
PEWCT1066	375	67
PEWCT1067	375	69
PEWCT1068	375	75
PEWCT1069	375	79
PEWCT1070	375	83
PEWCT1071	375	87
PEWCT1072	375	76
PEWCT1073	375	80
PEWCT1074	375	84
PEWCT1075	375	88
PEWCT1076	375	77
PEWCT1077	375	81
PEWCT1078	375	85
PEWCT1079	375	89
PEWCT1080	375	78
PEWCT1081	375	82
PEWCT1082	375	86
PEWCT1083	375	90
PEWCT1084	375	91
PEWCT1085	375	95
PEWCT1086	375	99
PEWCT1087	375	4
PEWCT1088	375	92
PEWCT1089	375	96
PEWCT1090	375	1
PEWCT1091	375	5
PEWCT1092	375	93
PEWCT1093	375	97
PEWCT1094	375	2
PEWCT1095	375	6
PEWCT1096	375	94
PEWCT1097	375	98
PEWCT1098	375	3
PEWCT1099	375	7
PEWCT1100	375	8
PEWCT1101	376	12
PEWCT1102	376	16
PEWCT1103	376	20
PEWCT1104	375	9
PEWCT1105	376	13
PEWCT1106	376	17
PEWCT1107	376	21
PEWCT1108	375	10
PEWCT1109	376	14
PEWCT1110	376	18
PEWCT1111	376	22
PEWCT1112	376	11
PEWCT1113	376	15
PEWCT1114	376	19
PEWCT1115	376	23
PEWG6056	378	1
PEWG6057	378	9
PEWG6058	378	10
PEWG6059	378	11
PEWG6060	378	12
PEWG6061	378	13
PEWG6062	378	14
PEWG6063	378	16
PEWG6064	378	17
PEWG6065	378	2
PEWG6066	378	3
PEWG6067	378	4
PEWG6068	378	5
PEWG6069	378	6
PEWG6070	378	7
PEWG6071	378	8
PEWGHW1000	389	83
PEWGHW1001	389	82
PEWGHW9000	389	81
PEWGK1000	388	24
PEWGK1001	388	32
PEWGK1002	388	34
PEWGK1003	388	36
PEWGK1004	388	40
PEWGK1005	389	46
PEWGK1006	389	48
PEWGK1007	389	47
PEWGK1008	389	54
PEWGK1009	389	56
PEWGK1010	389	55
PEWGK1011	389	62
PEWGK1012	389	64
PEWGK1013	389	63
PEWGK1014	388	23
PEWGK1015	388	31
PEWGK1016	388	33
PEWGK1017	388	35
PEWGK1018	388	39
PEWGK1019	389	43
PEWGK1020	389	45
PEWGK1021	389	44
PEWGK1022	389	51
PEWGK1023	389	53
PEWGK1024	389	52
PEWGK1025	389	61
PEWGK1026	389	59
PEWGK1027	389	60
PEWGN1010	381	37
PEWGN1011	381	38
PEWGN1012	381	36
PEWGN1013	381	39
PEWGS6000	377	43
PEWGS6001	377	45
PEWGS6002	377	42
PEWGS6003	377	44
PEWGS6004	377	51
PEWGS6005	377	53
PEWGS6006	377	50
PEWGS6007	377	52
PEWGS6008	377	55
PEWGS6009	377	57
PEWGS6010	377	54
PEWGS6011	377	56
PEWGS6012	377	59
PEWGS6013	377	61
PEWGS6014	377	58
PEWGS6015	377	60
PEWGS6016	378	71
PEWGS6017	378	73
PEWGS6018	378	70
PEWGS6019	378	72
PEWGS6020	378	83
PEWGS6021	378	85
PEWGS6022	378	82
PEWGS6023	378	84
PEWGS6024	378	87
PEWGS6025	378	89
PEWGS6026	378	86
PEWGS6027	378	88
PEWGS6028	378	95
PEWGS6029	378	97
PEWGS6030	378	94
PEWGS6031	378	96
PEWGS6032	378	91
PEWGS6033	378	92
PEWGS6034	378	90
PEWGS6035	378	93
PEWGS6036	378	75
PEWGS6037	378	77
PEWGS6038	378	74
PEWGS6039	378	76
PEWGS6040	377	47
PEWGS6041	377	49
PEWGS6042	377	46
PEWGS6043	377	48
PEWGS6044	379	20
PEWGS6045	379	22
PEWGS6046	379	19
PEWGS6047	379	21
PEWGS6048	379	24
PEWGS6049	379	26
PEWGS6050	379	23
PEWGS6051	379	25
PEWGS6052	378	99
PEWGS6053	378	18
PEWGS6054	378	98
PEWGS6055	378	15
PEWGS6056	377	38
PEWGS6057	377	39
PEWGS6058	377	40
PEWGS6059	377	41
PEWGS6060	377	62
PEWGS6061	377	64
PEWGS6062	378	66
PEWGS6063	378	68
PEWGS6064	377	63
PEWGS6065	377	65
PEWGS6066	378	67
PEWGS6067	378	69
PEWGS6068	378	78
PEWGS6069	378	79
PEWGS6070	378	80
PEWGS6071	378	81
PEWIR1000	381	40
PEWIR1001	381	41
PEWIR1002	381	42
PEWIR1003	381	43
PEWIR1004	381	44
PEWIR1006	381	50
PEWIR1007	381	49
PEWIR1008	381	48
PEWIR1009	381	47
PEWIR1010	381	46
PEWIR1015	381	45
PEWMT1000	382	53
PEWMT1001	382	54
PEWMT1002	382	55
PEWMT1003	382	56
PEWMT1004	382	57
PEWMT1005	382	58
PEWMT1006	382	59
PEWNS2000	318	6
PEWNS2001	318	7
PEWNS2002	318	8
PEWNS2003	318	9
PEWOT0001	382	60
PEWOT0003	382	61
PEWOT0007	382	62
PEWOT0009	382	63
PEWOT0014	382	64
PEWPL0000	383	76
PEWPL0005	383	77
PEWPL0008	383	78
PEWRD180B001	370	66
PEWRD180B002	370	67
PEWRD180S001-3	385	75
PEWRD180S001-6	385	76
PEWRD180TR1000	386	46
PEWRD180TW1001	387	96
PEWRD650B001	370	68
PEWRD650B002	370	69
PEWRD650S001-3	385	77
PEWRD650S001-6	385	78
PEWRD650TR1000	386	47
PEWRD650TW1001	387	7
PEWRD750B001	370	70
PEWRD750B002	370	71
PEWRD750S001-3	385	79
PEWRD750S001-6	385	80
PEWRD750TR1000

50-OHM CONVERSION TABLE

(dBm - volts- watts)

dBm	V	Po
+53	100.0	200W
+50	70.7	100W
+49	64.0	80W
+48	58.0	64W
+47	50.0	50W
+46	44.5	40W
+45	40.0	32W
+44	32.5	25W
+43	32.0	20W
+42	28.0	16W
+41	26.2	12.5W
+40	22.5	10W
+39	20.0	8W
+38	18.0	6.4W
+37	16.0	5W
+36	14.1	4W
+35	12.5	3.2W
+34	11.5	2.5W
+33	10.0	2W
+32	9.0	1.6W
+31	8.0	1.25W
+30	7.10	1.0W
+29	6.40	800 mW
+28	5.80	640 mW
+27	5.00	500 mW
+26	4.45	400 mW
+25	4.00	320 mW
+24	3.55	250 mW
+23	3.20	200 mW
+22	2.80	160 mW
+21	2.52	125 mW
+20	2.25	100 mW
+19	2.00	80 mW
+18	1.80	64 mW
+17	1.60	50 mW
+16	1.41	40 mW
+15	1.25	32 mW
+14	1.15	25 mW
+13	1.00	20 mW
+12	0.90	16 mW
+11	0.80	12.5 mW
+10	0.71	10 mW
+9	0.64	8 mW
+8	0.58	6.4 mW
+7	0.50	5 mW
+6	0.45	4 mW
+5	0.40	3.2 mW
+4	0.36	2.5 mW
+3	0.32	2.0 mW

dBm	V	Po
+2	0.28	1.6 mW
+1	0.25	1.25 mW
0	0.23	1.0 mW
-1	0.20	.80 mW
-2	0.18	.64 mW
-3	0.16	.50 mW
-4	0.14	.40 mW
-5	0.13	.32 mW
-6	0.12	.25 mW
-7	0.10	.20 mW
-8	0.09	.16 mW
-9	0.08	.125 mW
-10	0.07	.10 mW
-11	0.06	
-12	0.06	
-13	0.05	
-14	0.05	
-15	0.04	
-16	0.0355	
dBm	**mV**	**Po**
-17	31.5	
-18	28.5	
-19	25.1	
-20	22.5	.01 mW
-21	20.0	
-22	17.9	
-23	15.9	
-24	14.1	
-25	12.8	
-26	11.5	
-27	10.0	
-28	8.9	
-29	8.0	
-30	7.1	.001 mW
-31	6.25	
-32	5.8	
-33	5.0	
-34	4.5	
-35	4.0	
-36	3.5	
-37	3.2	
-38	2.85	
-39	2.5	
-40	2.25	.1 µW
-41	2.0	
-42	1.8	
-43	1.6	
-44	1.4	
-45	1.25	

dBm	mV	Po
-46	1.18	
-47	1.0	
-48	0.9	
-49	0.8	
-50	0.71	.01 µW
-51	0.64	
-52	0.57	
-53	0.5	
-54	0.45	
-55	0.4	
-56	0.351	
-57	0.32	
-58	0.286	
-59	0.251	
-60	0.225	.001 µW
-61	0.2	
-62	0.18	
-63	0.16	
-64	0.141	
dBm	**µV**	**Po**
-65	128	
-66	115	
-67	100	
-68	90	
-69	80	
-70	71	.1 nW
-71	65	
-72	58	
-73	50	
-74	45	
-75	40	
-76	35	
-77	32	
-78	29	
-79	25	
-80	22.5	.01 nW
-81	20	
-82	18	
-83	16	
-84	11.1	
-85	12.9	
-86	11.5	
-87	10.0	
-88	9.0	
-89	8.0	
-90	7.1	.001 nW
-91	6.1	
-92	5.75	
-93	5.0	

dBm	µV	Po
-94	4.5	
-95	4.0	
-96	3.51	
-97	3.2	
-98	2.9	
-99	2.51	
-100	2.25	.1 pW
-101	2.0	
-102	1.8	
-103	1.6	
-104	1.41	
-105	1.27	
-106	1.18	
dBm	**nV**	**Po**
-107	1000	
-108	900	
-109	800	
-110	710	.01 pW
-109	640	
-112	580	
-113	500	
-114	450	
-115	400	
-116	355	
-117	825	
-118	285	
-119	251	
-120	225	.001 pW
-121	200	
-122	180	
-123	160	
-124	141	
-125	128	
-126	117	
-127	100	
-128	90	
-129	80	
-130	71	.1 *f*W
-131	61	
-132	58	
-133	50	
-134	45	
-135	40	
-136	35	
-137	33	
-138	29	
-139	25	
-140	23	.01 *f*W

RETURN LOSS CONVERSION TABLE

Return Loss (dBm)	VSWR	Return Loss (dBm)	VSWR	Return Loss (dBm)	VSWR	Return Loss (dBm)	VSWR	Return Loss (dBm)	VSWR
46.064	1.01	13.842	1.51	9.485	2.01	7.327	2.51	5.999	3.01
40.086	1.02	13.708	1.52	9.428	2.02	7.294	2.52	5.970	3.02
36.607	1.03	13.577	1.53	9.372	2.03	7.262	2.53	5.956	3.03
34.151	1.04	13.449	1.54	9.317	2.04	7.230	2.54	5.935	3.04
32.256	1.05	13.324	1.55	9.262	2.05	7.198	2.55	5.914	3.05
30.714	1.06	13.201	1.56	9.208	2.06	7.167	2.56	5.893	3.06
29.417	1.07	13.081	1.57	9.155	2.07	7.135	2.57	5.872	3.07
28.299	1.08	12.964	1.58	9.103	2.08	7.105	2.58	5.852	3.08
27.318	1.09	12.849	1.59	9.051	2.09	7.074	2.59	5.832	3.09
26.444	1.10	12.736	1.60	8.999	2.10	7.044	2.60	5.811	3.10
25.658	1.11	12.625	1.61	8.949	2.11	7.014	2.61	5.791	3.11
24.943	1.12	12.518	1.62	8.899	2.12	6.984	2.62	5.771	3.12
24.289	1.13	12.412	1.63	8.849	2.13	6.954	2.63	5.751	3.13
23.686	1.14	12.308	1.64	8.800	2.14	6.925	2.64	5.732	3.14
23.127	1.15	12.207	1.65	8.752	2.15	6.896	2.65	5.712	3.15
22.607	1.16	12.107	1.66	8.705	2.16	6.867	2.66	5.693	3.16
22.120	1.17	12.009	1.67	8.657	2.17	6.839	2.67	5.674	3.17
21.664	1.18	11.913	1.68	8.611	2.18	6.811	2.68	5.654	3.18
21.234	1.19	11.818	1.69	8.565	2.19	6.783	2.69	5.635	3.19
20.828	1.20	11.725	1.70	8.519	2.20	6.755	2.70	5.617	3.20
20.443	1.21	11.634	1.71	8.474	2.21	6.728	2.71	5.598	3.21
20.079	1.22	11.545	1.72	8.430	2.22	6.700	2.72	5.579	3.22
19.732	1.23	11.457	1.73	8.386	2.23	6.673	2.73	5.561	3.23
19.401	1.24	11.370	1.74	8.342	2.24	6.646	2.74	5.542	3.24
19.085	1.25	11.285	1.75	8.299	2.25	6.620	2.75	5.524	3.25
18.783	1.26	11.202	1.76	8.257	2.26	6.594	2.76	5.506	3.26
18.493	1.27	11.120	1.77	8.215	2.27	6.567	2.77	5.488	3.27
18.216	1.28	11.039	1.78	8.173	2.28	6.541	2.78	5.470	3.28
17.949	1.29	10.960	1.79	8.138	2.29	6.516	2.79	5.452	3.29
17.690	1.30	10.881	1.80	8.091	2.30	6.490	2.80	5.435	3.30
17.445	1.31	10.804	1.81	8.051	2.31	6.465	2.81	5.417	3.31
17.207	1.32	10.729	1.82	8.011	2.32	6.440	2.82	5.400	3.32
16.977	1.33	10.654	1.83	7.972	2.33	6.415	2.83	5.383	3.33
16.755	1.34	10.581	1.84	7.933	2.34	6.390	2.84	5.365	3.34
16.540	1.35	10.509	1.85	7.894	2.35	6.366	2.85	5.348	3.35
16.332	1.36	10.437	1.86	7.856	2.36	6.341	2.86	5.331	3.36
16.131	1.37	10.367	1.87	7.818	2.37	6.317	2.87	5.315	3.37
15.936	1.38	10.298	1.88	7.781	2.38	6.293	2.88	5.298	3.38
15.747	1.39	10.230	1.89	7.744	2.39	6.270	2.89	5.281	3.39
15.563	1.40	10.163	1.90	7.707	2.40	6.246	2.90	5.265	3.40
15.385	1.41	10.097	1.91	7.671	2.41	6.223	2.91	5.248	3.41
15.211	1.42	10.032	1.92	7.635	2.42	6.200	2.92	5.232	3.42
15.043	1.43	9.968	1.93	7.599	2.43	6.177	2.93	5.216	3.43
14.879	1.44	9.904	1.94	7.564	2.44	6.154	2.94	5.200	3.44
14.719	1.45	9.842	1.95	7.529	2.45	6.131	2.95	5.184	3.45
14.564	1.46	9.780	1.96	7.494	2.46	6.109	2.96	5.168	3.46
14.412	1.47	9.720	1.97	7.460	2.47	6.086	2.97	5.152	3.47
14.264	1.48	9.660	1.98	7.426	2.48	6.064	2.98	5.137	3.48
14.120	1.49	9.601	1.99	7.393	2.49	6.042	2.99	5.121	3.49
13.979	1.50	9.542	2.00	7.360	2.50	6.021	3.00	5.105	3.50

MOUNTING HOLES



CODE	A	B	C
A01	.500	.340	.102
A02	.687	.500	.109
A03	.687	.500	#3-56 TAP
A04	.687	.500	.125
A05	1.000	.718	.125
A06	.750	.531	.140
A07	.750	.531	.125
A08	1.190	.906	.125
A09	.687	.500	#4-40 TAP
A10	.687	.500	.136
A11	1.250	.975	.147
A12	2.000	1.440	.257
A13	1.000	.718	.141
A14	1.000	.718	.144
A15	.687	.500	.104
A16	.750	.531	.136
A17	.375	.232	.067
A18	.625	.437	.094
A19	1.000	.718	#6-32 TAP
A20	.500	.340	#2-56 TAP
A21	1.250	.975	.142
A22	.375	.232	.093



CODE	A
F01	.250
F02	.500
F03	.630
F04	1.200
F05	.380
F06	.450
F07	.200
F08	.362
F09	.220
F10	.317
F11	4.83mm
F12	.390



CODE	A	B
B01	.195	.177
B02	.250	.235
B03	.330	.295
B04	.380	.350
B05	.440	.410
B06	.512	.480
B07	.760	.720
B08	.565	.537
B09	.314	.296
B10	.140	.126
B11	.695	.655
B12	.625	.575
B13	.405	.361
B14	.277	.252
B15	.630	.596
B16	.317	.285
B17	.284	.268



CODE	A	B
J01	.200	.046



CODE	A	B	C
D01	.200	.067	.062
D02	.200	.067	.046
D03	.100	.031	.031
D04	.200	.052	.052
D05	.260	.067	.043
D06	.200	.052	.047
D07	.200	.055	.043
D08	.200	.067	.035
D09	.200	.055	.028
D10	.200	.055	.035
D11	.320	.091	.031
D12	.400	.062	.062
D13	.320	.091	.091
D14	.340	.091	.043
D15	.164	.067	.091
D16	.500	.126	.440
D17	.380	.083	.043



CODE	A	B	C
C01	.223	.481	.102
C02	.260	.481	.102
C03	.192	.328	.067
C04	.640	1.000	.125
C05	.275	.481	.102
C06	.230	.354	.067
C07	.188	.328	.093



CODE	A	B
G01	.640	.546
G02	.380	.340
G03	.765	.712
G04	.362	.323
G05	.236	.197
G06	.217	.177
G07	.380	.310
G08	1.161	1.000



CODE	A	B	C	D	E
E01	.375	.500	.340	.222	.093



CODE	A	B	C	D
H01	.687	.500	.125	.045

Appendix

CONNECTOR IDENTIFIER

SPECIFICATIONS SHOWN ARE INTENDED FOR IDENTIFICATION PURPOSES ONLY



*SMA, 2.92mm, & 3.5mm CONNECTORS WILL MATE MECHANICALLY & ELECTRICALLY TO EACH OTHER. **1.85mm & 2.4mm CONNECTORS WILL MATE MECHANICALLY & ELECTRICALLY TO EACH OTHER.

CONNECTOR IDENTIFIER

SPECIFICATIONS SHOWN ARE INTENDED FOR IDENTIFICATION PURPOSES ONLY

BNC TWINAX

PLUG



JACK



C

MALE



FEMALE



D SUBMINIATURE

PLUG



RECEPTACLE



F

MALE



FEMALE



FAKRA

PLUG



FAKRA

JACK



FAKRA

COMPLETE KEY CODE INFO

CODE	JACK	PLUG	COLOR	APPLICATION
A			BLACK	RADIO WITH PHANTOM SUPPLY
B			WHITE	RADIO WITHOUT PHANTOM SUPPLY
C			BLUE	GPS: TELEMATICS OR NAVIGATION
D			BORDEAUX	GSM: CELLULAR PHONE

CODE	JACK	PLUG	COLOR	APPLICATION
H			VIOLET	GPS: TELEMATICS AND NAVIGATION
I			BEIGE	BLUETOOTH
K			CURRY	RADIO WITH I.F. OUTPUT (ANTENNA DIVERSITY)
Z			WATER BLUE	NEUTRAL CODING

FME

PLUG



JACK



GR874



HN

MALE



FEMALE



LC

MALE



FEMALE



UMCX

PLUG



JACK



MC-CARD



MCX

PLUG



JACK



CONNECTOR IDENTIFIER

SPECIFICATIONS SHOWN ARE INTENDED FOR IDENTIFICATION PURPOSES ONLY



Appendix

CONNECTOR IDENTIFIER

SPECIFICATIONS SHOWN ARE INTENDED FOR IDENTIFICATION PURPOSES ONLY

SHV

PLUG



JACK



SMA*

MALE



FEMALE



REVERSE POLARITY SMA

MALE



FEMALE



SMA REVERSE THREAD

MALE



FEMALE



SMB

PLUG



JACK



75 OHM SMB

PLUG



JACK



SMC

PLUG



JACK



75 OHM SMC

PLUG



JACK



SMP

MALE



FEMALE



SSMA

MALE



FEMALE



SSMB

PLUG



JACK



TNC

MALE



FEMALE



75 OHM TNC

MALE



FEMALE



REVERSE POLARITY TNC

MALE



FEMALE



UHF

MALE



FEMALE



*SMA, 2.92mm & 3.5mm CONNECTORS WILL MATE MECHANICALLY & ELECTRICALLY TO EACH OTHER.

CONNECTOR FREQUENCY RANGE CHART



Notes:

1: BNC-75 Ohm connectors operate up to 1 GHz
2: SMB-75 Ohm & Mini SMB-75 Ohm connectors operate up to 4 GHz
3: MCX-75 Ohm connectors operate up to 6 GHz
4: SMC-75 Ohm connectors operate up to 10 GHz
5: N-75 Ohm connectors operate up to 1.5 GHz
6: TNC-75 Ohm connectors operate up to 1 GHz

PASTERNACK®
an INFINITE brand

RF Solutions from RF Engineers

Authorized Pasternack Distributor:

SPECTECH LIMITED
TEL: +44 0 1420 544789
FAX: +44 0 1420 544788
EMAIL: sales@spectechlimited.com
WEB: www.spectechlimited.com

Same-Day Shipping
on orders placed by 4:00 pm PST

24-Hour Support
by phone, chat or email

Secure Online Ordering
pasternack.com
sales@pasternack.com

USA & Canada: 1 (866) 727-8376
International: +1 (949) 261-1920